

FEATURES

- Available in 8 sizes
- Ergonomic soft-grip handles & premium-quality plastics for a comfortable grip
- Phosphate coated tip for increased friction on fixings, reducing the risk of rounding or damaging the screws

RS PRO Flat Standard Screwdriver (Cabinet Tip)

RS Stock No.: 1829661



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.

Product Description

Introducing cabinet tip slotted screwdrivers from our trusted and reliable own brand RS PRO, a range of durable screwdrivers suitable for use with slotted screws and terminals. The screwdrivers feature a chrome vanadium molybdenum steel blade with a matt chrome finish, providing long life and corrosion resistance properties. These durable screwdrivers also feature an ergonomic soft grip handle for enhanced comfort and grip, assisting with torque.

RS Pro also provides a range of screwdrivers with larger tip sizes, featuring a flared tip for optimal strength in higher torque applications.

Features and benefits

- Made with durable Chrome Vanadium Molybdenum steel providing excellent durability
- Matte chrome finish for excellent corrosion resistance
- Black tip for distinct contrast between screw and tip
- Cabinet tip for optimal use when reaching into confined spaces where screws are recessed
- Soft grip handle for enhanced grip and control
- Ideal for use with terminals
- Available in a variety of sizes

Common applications

Slotted screwdrivers with cabinet tips are an essential hand tool in many tool kits, used in a wide range of applications such as:

- Construction
- DIY
- Industrial
- Electrical
- Automotive

General Specifications

Screwdriver Type	Slotted Head; Ergonomic; Standard; Rounded Blade
Number of Pieces	1
Tip Type	Straight; Slotted; Flat; Cabinet Tip

Electrical Specifications

ESD Safe	No
-----------------	----

Mechanical Specifications

Tip Size	2.5 mm; 3 mm; 3.5 mm; 4 mm
Blade Length	75 mm; 100 mm; 125 mm; 150 mm
Overall Length	165 mm; 175 mm; 190 mm; 200 mm; 225 mm; 250 mm
Blade Material	Chrome Vanadium Molybdenum Steel
Handle Material	Rubberised Soft Grip; PPE; TPE
Blade Shape	Round
Blade Finish	Black Phosphate; Black Tip; Chrome

Available sizes in range

Stock No.	Product Name	Tip Size (mm)	Blade Length (mm)	Overall Length (mm)
1829658	Slotted Screwdriver (Cabinet Tip)	2.5	75	165
1829659	Slotted Screwdriver (Cabinet Tip)	3.0	75	165
1829660	Slotted Screwdriver (Cabinet Tip)	3.0	100	190
1829661	Slotted Screwdriver (Cabinet Tip)	3.5	100	190
1829662	Slotted Screwdriver (Cabinet Tip)	4.0	75	175
1829663	Slotted Screwdriver (Cabinet Tip)	4.0	100	200
1829664	Slotted Screwdriver (Cabinet Tip)	4.0	125	225
1829665	Slotted Screwdriver (Cabinet Tip)	4.0	150	250

Approvals

IEC Name	DIN ISO 2380-1
-----------------	----------------

Similar Products

Parameters	1829682
Brand	RS PRO
Screwdriver Type	Hex Bolster
Number of Pieces	1
Tip Type	Slotted
ESD Safe	No
Tip Size	10mm
Blade Length	175mm
Blade Material	Chrome Vanadium Molybdenum
Overall Length	220mm
Handle Material	PPE/TPE
Blade Finish	Chrome
Special Features	Hex Bolster
Blade Shape	Flared
IEC Name	DIN ISO 2380-1





