



Unicare Soft Nitrile (GS004*)

blue · medical grade · light weight · nitrile examination gloves

Physical Specifications:

Material: Nitrile (latex free)
Colour: Blue
Length: 240 mm
Weight: 3.5 g
Thickness: 0.08 mm
Finish: Powder free, chlorinated
Fit: Ambidextrous
Sterile: No

Order Codes and Size Information:

GS0041 | Extra small
GS0042 | Small
GS0043 | Medium
GS0044 | Large
GS0045 | Extra large

Packaging:

Each dispenser box contains 200 gloves
Each case contains 10 dispenser boxes

Classification:



AQL 1.5 (Pinholes) EN455 (Medical Grade)



Food Safe EN374-3 EN374-2

For more about the Unicare range, please click on the image



Features

- Tested to EN374
- AQL 1.5
- Free from powder
- Free from phthalates
- Tested to EN1186
- Nitrile formulation conforms to the hand during use
- Beaded cuff
- Manufactured with textured fingertips
- Lightweight construction

Benefits

- Resistant to a range of chemicals
- Meets medical standards for pinholes
- Reduces risks of latex allergies (Type I sensitisation) and minimises particulate contamination
- Suitable for contact with food
- Suitable for contact with all food types
- Nitrile formulation conforms to the hand during use for a more comfortable fit
- Beaded cuff provides extra strength during donning and helps prevent liquid roll back
- Textured palms and fingertips provide improved grip, particularly when working in wet or oily conditions
- Lightweight construction provides good tactile sensitivity with reduced cost

Sectors

- Care home work
- Cleaning and janitorial
- Dentistry · Dental hygiene
- Emergency services
- Food processing
- General assembly
- Healthcare · Hospital and clinical duties
- Janitorial · Local Authority work
- Painting and decorating · Printing

