

EKJB MPI 130G



Sample image

Order symbol : EKJB MPI 130G

Product nr : 2538213

Description : Enclosure, PC

Remarks : Grey cover

EAN : 6418074321046

El. number :

- Finland : 3424764
- Denmark : 8212010275
- Sweden : 2507747

Including : Flanged Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws. Including plastic mounting plate.

Dimensions :	Height	Width	Depth
mm :	280	190	130
inch :	11.02	7.48	5.12

Materials :

Material :	Polycarbonate
Base colour :	RAL_7035
Cover colour :	RAL 7035 -light grey
Gasket material :	Polyurethane

Ratings :

Ingress protection (EN 60529):	IP66/67;
Impact Resistance (EN 62262):	IK08;
electrical_insulation :	Totally insulated
Halogen free (DIN/VDE 0472, Part 815) :	Yes
UV resistance :	UL 746C
Flammability Rating :	UL 94 V0
Glow Wire Test (IEC 695-2-1) °C :	960C

Temperatures :

Temperature °C (continuous) :	-40 ... 80
Temperature °F (continuous) :	-40 ... 175