



Datasheet RS PRO P 303018 T + MP 3030, Polyester, 300x300x175mm

Stock No: 508-324





Sample photo

+

Technical Specifications:

Material	Polyester
Dimensions (LxWxH)	300x300x175mm
Colour	Base: RAL 7036 – light grey Cover: Transparent
IP Rating	IP 66
IK Rating	IK 10
Electrical insulation	Totally insulated
Flammability Rating	UL 746C 5"

rspro.com

Features & Benefits:

- Halogen free
- Good UV resistance
- Good chemical resistance
- Temperature Range from -50° to +160°, short term
- Temperature Range from -40° to +80°, continuous

• Including:

Base, mountingplate, screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws. The cabinets were designed and tested for wall-/pole mounting in upright position.

Dimensional line drawings





