



## PRODUCT-DETAILS

**BGM0606****STR BRASS FITTING M32 32MM-MET****General Information**

Extended Product Type:	BGM0606
Product ID:	7TCA297020R0060
EAN:	5011949200500
Catalog Description:	STR BRASS FITTING M32 32MM-MET
Long Description:	Fitting for Pliable Conduit, Straight with External Male Thread, Conduit Size 32mm, M32 Thread, Very High Mechanical and UV Protection, IP66, IP67 Ratings, Brass to BS2874 with Nylon Seals
Display Name:	BGM0606

**Additional Information**

Product Main Type:	KOPEX-EX FLEXIBLE CABLE PROTECTION
Application:	For Insertion Into Threaded Entries and Knockouts Using a Locknut to Secure

**Ordering**

EAN:	5011949200500
UPC:	786210267845

**Technical**

Number of Batteries:	0
Color:	Metallic
Material:	Brass with Nylon Seals
Size:	Conduit Size 32mm ; M32 Thread

**Environmental**

WEEE Category:	Product Not in WEEE Scope
----------------	---------------------------

**RoHS Information:** Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019

---

---

## Container Information

---

<b>Package Level 1 Units:</b>	5 piece
<b>Package Level 1 EAN:</b>	5011949200500
<b>Package Level 1 Height:</b>	1 in 25 mm
<b>Package Level 1 Depth / Length:</b>	1 in 25 mm
<b>Package Level 1 Width:</b>	1 in 25 mm

---

---

## Certificates and Declarations

---

<b>Declaration of Conformity - CE:</b>	9AKK107492A9617
<b>RoHS Declaration:</b>	9AKK107992A8994
<b>REACH Declaration:</b>	9AKK107992A8994

---

---

## External Classifications and Standards

---

<b>ETIM 8:</b>	EC001180 - Screw connection for protective metallic hose
<b>ETIM 9:</b>	EC001180 - Screw connection for protective metallic hose
<b>UNSPSC:</b>	39121311

---

---

## Categories

---

Products > Low Voltage Products and Systems > Installation Products > Cable Protection, Explosion Proof and Lighting > Flexible Cable Protection Systems