

SPRAY LANCE

33-inch / 850 mm stainless steel lance (manual coupling) with ergonomic handle for ease of use and protection. Rotatable 360° under pressure.



Order no. 4.112-006.0

Technical data

EAN code		4054278173979
Length	mm	840
Temperature	°C	max. 155
Connecting thread		EASY!Lock
Weight incl. packaging	kg	0.9

COMPATIBLE MACHINES

- HD 10/21-4 S *KAP
- HD 10/23-4 S *MX
- HD 10/25-4 S
- HD 10/25-4 S *KAP
- HD 728 B Cage
- HD 9/21 G
- HD 9/23 De
- HD 9/23 G
- HD Super Class
- HDS 10/20 -4M Classic *KAP
- HDS 1000 Be
- HDS 1000 De
- HDS 1000 De CEMO
- HDS 12/18 -4S Classic *KAP
- HDS 3.5/30-4 M Ea
- HDS 4.5/22-4 M Ea
- HDS 6/14 C Classic *KAP
- HDS 7/11-4M Classic *KAP
- HDS 7/16 C Classic *KAP
- HDS 8/18 4C Classic *KAP
- HDS 9/18-4 M Classic *KAP
- HDS Mid Class
- HDS Special Class
- HD 5/11 EX Plus Classic
- HD 5/13 EX Plus Classic
- HD 5/13 E Classic
- Pro HD 400
- HD 4/9 P
- HD 5/12 C
- HD Compact Class
- HD
- HD 6/15 MX Plus *CH
- HD 8/18-4M *KAP
- HD Special Class
- HD 4/10 AKKU-HD C
- HDS Upright Class
- HDS 5/13 U
- HDS 8/18-4 C Classic *KAP
- HD 8/20 G
- HD 7/15 G
- HDS 8/20 G *EU
- HDS 8/20 D *EU