

4 Port DVI USB KVM Switch with Audio & USB Hub

Product ID: SV431DVIUAGB



This 4 port DVI USB KVM Switch lets you control four USB enabled, DVI capable computers from a single USB keyboard and mouse peripheral set.

Ideal for multimedia applications, the switch supports audio and microphone switching, allowing you to switch between audio/mic channels either independently or simultaneously when switching between computers for KVM control.

The DVI USB KVM switch features an integrated USB 2.0 hub which allows you to use shared USB peripherals from the control point as if the devices were connected directly to the slave computers - an economical solution that lets you use USB peripherals between computers (when selected) without the expense of buying individual peripherals for each slave computer.

Rackmount your KVM switch

If you'd like to mount this KVM switch to your server rack, StarTech.com offers a 1U Rackmount Bracket (sold separately) that turns this KVM into a rackmountable KVM.

This product is TAA compliant and is backed by a StarTech.com 3 year warranty with lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Ideal for using desktops, workstations and servers with Flat Panel LCD monitor
- Sharing computers and USB devices in the home/SOHO/multimedia environment
- Switches instantly between PCs
- Switching USB peripherals between PC's

Features

- 4-port DVI USB KVM switch with audio and microphone switching and 2 x USB 2.0 hub ports
- Channel selection/Hub port control by front-panel push buttons
- DVI interface technology supports digital video signal transmission
- Independent/simultaneous USB hub port, audio & mic channels and PC port selection
- USB keyboard and mouse support
- HDCP Compliant

Hardware	Warranty	3 Years	
	Audio	Yes	
	Cables Included	No	
	Daisy-Chain	No	
	KVM Ports	4	
	Number of Monitors Supported	1	
	PC Interface	USB	
	PC Video Type	DVI	
	Rack-Mountable	Optional	
Performance	DVI Support	Yes	
	Hot-Key Selection	No	
	IP Control	No	
	Maximum Analog Resolutions	2560x1600 @ 60Hz	
	Maximum Digital Resolutions	1920x1200 @60/70Hz	
	Maximum Number of Users	1	
	MTBF	143000 hours	
	On-Screen Display	No	
	Port Selection Support	Push Button	
Connector(s)	Console Interface(s)	1 - DVI-I (29 pin) Female 2 - 3.5 mm Mini-Jack (3 Position) Female 2 - USB Type-A (4 pin) USB 2.0 Female	
	Host Connectors	4 - DVI-I (29 pin) Female 4 - USB B (4 pin) Female 8 - 3.5 mm Mini-Jack (3 Position) Female	
	Other Interface(s)	2 - USB Type-A (4 pin) USB 2.0 Female	
	Software	OS Compatibility	OS independent; No software or drivers required
	Power	Center Tip Polarity	Positive
Input Current		0.4A	
Input Voltage		110V-240V AC	
Output Current		2A	
Output Voltage		5 DC	
Plug Type		N	

	Power Consumption (In Watts)	10
	Power Source	AC Adapter Included
Physical Characteristics	Color	Black
	Enclosure Type	Steel
	Product Depth	115 mm [4.5 in]
	Product Height	45 mm [1.8 in]
	Product Weight	1000 g [35.3 oz]
	Product Width	253 mm [10 in]
	Packaging Information	Shipping (Package) Weight
What's in the Box		Included in Package
		1 - Pack Rubber Feet
		1 - Power Adapter
		1 - User Manual

Product appearance and specifications are subject to change without notice.