



LSTTR 2.4

E0776002.

SHRINK TUBE WITHOUT ADHESIVE, 2:1, ID=2.4mm BLACK, BOX, L=10.0m, THIN-W

Product Properties:

Model	Thin-walled
Operating temperature	-40-105 °C
Transparent	No
Type	Heat-shrink
Shrink rate	2:1
With inner glue	No
Printable	No
Colour	Black
Material	Polyolefin (PO-X)
Halogen free	No

Dimensions:

Wall thickness after shrinking	0.55 mm
MOQ	1 .
Unit	pcs
Length	10 m
Nominal diameter inch	3/32 inch
Inner diameter before heat-shrink	2.4 mm
Inner diameter after heat-shrink	1.2 mm

Approvals:

UL approval	No
-------------	----

Compliance:

Conflict Minerals	N/A, Contains no conflict minerals
Iron and Steel Sanction	Compliance
Link to manufacturer COC	https://www.te.com/commerce/alt/SinglePartSearch.do?PN=7284836003
REACH	No SVHC (241 Subs. 27 June 2024)
RoHS	RoHS 3 (2015/863)
SCIP	Not Applicable
US TSCA	No (5 PBT Subs, Feb 2021)
ECCN (EU)	No CLASS
ECCN (US)	EAR99

Other information:

ETIM-Class	EC000217 - Shrink tubing
ETIM-Release	10.0
Trademark	TE Connectivity
Product Group	Minibox
Search Description	7284836003
Alternative SKU	LSTTR2.4
E-no	E0776002.

Logistic information:

Barcode	501745500072
Country of origin	CZ
E-no	E0776002.
Item status	Non Stock Item, can be on stock but is not a regular stock item.
MOQ	1 .
Stock code	LSTTR 2.4
Taric code	39173200
Unit	pcs

*We reserve the right to make technical changes and disclaim any typographical errors.