

Technical sheet

BAR4006NJ

Expandable steel barrier - 6 castors - 4 m - black/yellow

Extendable barrier with a maximum length of 4 meters and a fixed foot. Used to demarcate hazardous areas and prevent access to limit accident risks. Made of painted steel with epoxy paint, it's easily foldable thanks to its rivet system. Compact when folded for space-saving storage. Possibility to screw an information panel onto the barrier.





Customs code	7326909890
EAN	3321360038302

Color : Black/Yellow

Material : Steel

Specifications :

- Extendable barrier up to 4.0 m.
- Six wheels with brakes for easy maneuverability.
- Multiple barriers can be linked together using a simple hook system.
- Folds in the middle to protect an angled area (between 30° and 180°) up to 2 m.
  A hook secures the crossbars in a locked position during storage and transport.
- An A4 display panel (RSA4PN optional) can be attached to the center of the barrier.

Length (mm)	Width (mm)	Height (mm)	Unfolded dimensions (mm)	Net weight (kg)
4000	450	1080	4000 x 450 x 1000	21,10

VISO
www.viso-cpn.com

VISO - 7 avenue Arago - ZI de la Vigne aux Loups - 91380 CHILLY-MAZARIN - France
Tél. + 33 (0)1 69 53 46 70 - Fax + 33 (0)1 69 53 46 80 - contact@viso-cpn.com / commande@viso-cpn.com