

Features

- Deep Groove Ball Bearing Design
- Pressed Steel Cage
- Both Side Sealed

RS PRO Ball Bearings

RS Stock No.: 0291712



RS PRO is the own brand of RS. The RS PRO Seal of Approval is your assurance of professional quality, a guarantee that every part is rigorously tested, inspected, and audited against demanding standards. Making RS PRO the Smart Choice for our customers.

Product Description

A Comprehensive range of Deep Groove Ball Bearings offering versatility and overall high performance. Deep Groove Ball Bearings are the most widely used bearing and are utilised in a huge variety of applications, environments, and sectors.

General Specifications

Ball Bearing Type	Deep Groove
Sealing Arrangement	Both Side Sealed
Number of Rows	1
Material	Steel
Ball Material	Steel
Cage Material	Steel
Race Material	Steel
Race Type	Plain
Bore Type	Parallel
Seals / Shields	Sealed
Clearance	CN
Bearing Series	8 Extra Thin Section

Mechanical Specifications

Inside Diameter	45mm
Outside Diameter	68mm
Race Width	12mm
Static Load Rating	10.9kN
Dynamic Load Rating	14.1kN
Limiting Speed	9700 r/min
Mass	0.14 Kg

