



PW3 HI-VIS COTTON COMFORT T-SHIRT S/S

DESCRIPTION

Constructed using premium HiVisTex Pro tape, this Cotton Comfort t-shirt offers excellent freedom of movement due to its segmented tape design. Lightweight, stylish and breathable, this t-shirt is the perfect choice.

COMPOSITION

55% Cotton, 45% Polyester, Knit, 175g
 Orange/Black XS-6XL

FEATURES

- Moisture wicking fabric helping to keep the body cool and dry
- High cotton content for superior comfort
- Side vents for added comfort
- Crew neck
- Designed with a comfort fit
- Heat applied segmented reflective tape for added visibility
- Chest pocket
- 40+ UPF rated fabric to block 98% of UV rays
- Certified to EN ISO 20471 after 50x washes
- Complies with RIS 3279-TOM for rail industry (orange only)
- CE certified
- UKCA marked

STANDARDS

EN ISO 20471 Class 2
RIS 3279 TOM Issue 2 (Orange Only)
ANSI/ISEA 107 Type R Class 2
ANSI/ISEA 107 TYPE P CLASS 2

COLOUR / SIZES

SKU	COLOUR	SIZE RANGE
T181OBR	ORANGE/BLACK	XS-6XL

FEATURES

x1
1 POCKET
1 pocket for secure storage

HEAT APPLIED SEGMENTED REFLECTIVE TAPE
This symbol indicates that the garment has heat applied reflective tape

CERTIFIED AFTER 50X WASHES
Certified to EN ISO 20471 after 50x washes



STANDARDS



EN ISO 20471
High Visibility Clothing - Test Methods
And Requirements




PERFORMANCE WORKWEAR

PW3™ contemporary workwear blends sports and lifestyle trends with function, a modern fit and improved comfort.

GET THE COLLECTION



TECHINCAL INFORMATION



SATRA Technology Europe Ltd
(Notified Body Number.: NB: 2777)
Bracetown Business Park Clonee Dublin
15 D15 YN2P, Ireland Cert No:
2777/11506-03/E00-00

SATRA Technology Centre Ltd
(Notified Body Number.: AB: 0321) SATRA
Technology Park Wyndham Way Telford
Way Kettering Northamptonshire NN16
8SD, United Kingdom Cert No:
AB0321/16795-01/E00-00

OEKO-TEX certification
11-34354

Item	Colour Fit	Len (cm)	Wid (cm)	Hgt (cm)	Weight (Kg)	Cubic (m ³)	EAN13	GTIN/DUN14
T181OBRXS	Orange/Black	55	36	37	.254	1526.250	5036108306916	15036108795991
T181OBRBS	Orange/Black	55	36	37	.278	1526.250	5036108287888	15036108778024
T181OBRBM	Orange/Black	55	36	37	.284	1526.250	5036108287871	15036108778017
T181OBRBL	Orange/Black	55	36	37	.298	1526.250	5036108287864	15036108778000
T181OBRXL	Orange/Black	55	36	40	.310	1650.000	5036108287895	15036108778031
T181OBRXXL	Orange/Black	55	36	40	.332	1650.000	5036108287901	15036108778048
T181OBRXXXL	Orange/Black	55	36	40	.338	1650.000	5036108287918	15036108778055
T181OBR4XL	Orange/Black	55	36	40	.360	1650.000	5036108297092	15036108786821
T181OBR5XL	Orange/Black	55	36	40	.372	1650.000	5036108346851	15036108835420
T181OBR6XL	Orange/Black	55	36	40	.999	1650.000	5036108512195	15036108997289