

Programmeur universel de production, 4 supports 48 broches (expandable à 144 broches) sur port USB, (version économique).

# SUPERPRO<sup>®</sup> / 5004EGP

Universal Programmer

Supporte les EPROMS/EEPROMS/FLASH/PLD/Microcontrôleurs

Plus de 76.000 composants supportés



#### Présentation :

Le SuperPro-5004EGP est un programmeur universel pour la production équipé de 4 supports ZIF48 broches et supportant plus de 76.000 références de composants de plus de 290 fabricants. Il fonctionne sur port USB2.0 ce qui lui permet une vitesse de programmation ultra rapide. Les 4 supports sont indépendants et permettent de programmer 4 composants identique simultanément. Sur chacun des supports, la programmation du composant démarre automatiquement dès lors que celui-ci est positionné et verrouillé sur le support. Le programmeur effectue également un test sur les pattes du composant inséré afin de détecter d'éventuelles anomalies : composant inséré à l'envers, patte défectueuse. Il ne nécessite aucun adaptateur pour tous les composants en boîtiers DIP jusqu'à 48 broches. Au delà il peut gérer grâce à ses supports interchangeable, les composants ayant jusqu'à 144 broches programmables! Les composants basse tension jusqu'à 1,2V sont également supportés. Il permet des fonctions avancées de production comme la programmation automatique dès que le composant est détecté sur le support, la vérification du code d'identification du composant, génération de numéros de séries automatique dans le composant. Il permet des fonctions avancées de production comme la programmation automatique dès que le composant est détecté sur le support, la vérification du code d'identification du composant, génération de numéros de séries automatique dans le composant. Le logiciel livré sur CD-ROM fonctionne sous Windows 98/2000/XP/VISTA/Win7/Win8 (32/64bits) et les mises à jour du logiciel et des algorithmes sont téléchargeables gratuitement sur Internet.

#### Contenu :

Un programmeur. Un bloc d'alimentation 85-260Vac / 12Vdc. Un cordon USB type A-B. Un logiciel sur CD.  
Un mode d'emploi en Français et en Anglais.

#### Options :

ISP-HEADER-10 : adaptateur ISP/ICP pour la programmation en In-Situ.  
Adaptateurs universels PLCC, SO, QFP, BGA, etc... (Consulter la rubrique adaptateurs).

Compatible Windows XP / VISTA / Win7 / Win8 (32/64 bits)

Informations produits : [www.seeit.fr](http://www.seeit.fr)

Distributeurs : [www.rs-components.com](http://www.rs-components.com)

↓ Liste des composants programmés ↓



**LISTE DES COMPOSANTS SUPPORTES SuperPro-5004EGP**  
(Programmateur universel de production, driver 144 broches)

Appuyer sur "CTRL + F" pour rechercher un composant

Programmateur universel SuperPro-5004EGP

Nombre de fabricants : 294

Nombre de composants : 76882

version 10.0

Explications pour lire une référence

Exemple: 24LC16B@SOIC8 [CX1045]

24LC16B: nom du composant

@SOIC8: type de boîtier

[CX1045]: nom de l'adaptateur (si nécessaire)

**Fabricants:**

ABOV	ACE Technology	ACT	ACTRANS
ADESTO	ADI	ADVANCE GROUP	
AiT Semiconductor		ALI (Acer)	ALL24SERIES
ALLFLASH	ALLIANCE	ALTCO	ALTERA
AMD	AMIC	AMS	ANACHIP
APLUS FLASH	ARTSCHIP	ASAHI KASEI (AKM)	ASD
ASI	Asic Microelectronics		ASP
ASTIGP-MICROCHIP	ATC	ATMEL	ATMEL W&M
ATMEL-CUSTOM	ATMEL-CUSTOMER	ATO	AUO
AUSTIN	AXELITE	AZOTEQ	BELLING
BENCHMARQ	BERGMICRO	BJX	BMT
BOCH	Bookly Micro	BRIGHT	CATALYST
CBC Microelectronics		CERAMATE	CETC58
CFEON	CHINA CORE	CHINGIS	CHIPCON
CHIPMAST	CHIPON	CHIPSWINNER	CKD Technology
CORERIVER	CUSTOMER	CWI	CYGNAL
CYPRESS	CYROD	DALLAS	DENSE-PAC
DEUTRON	E-CMOS	EETI	EFST
eGalax	ELECTRONIC ARRAYS		EM
EMTC	ENERGY	EON	EOREX
EPSON	ESMT	ESTEK	E-TRAND
EVERSPIN	EVERSTAR	EXCELSEMI	EXEL
FAIRCHILD	FDI	FIDELIX	
FIRST-RANK Technology		FLEXTRONICS	
FORCE TECHNOLOGIES		FORCREAT	FORWARD
FREESCALE	Fremont Micro Devices		FTDICHIP
FUDAN	FUJITSU	FULLRICH	GAMMA
GATELEVEL	GENCORE	GENERAL (GI)	GENERALPLUS
GENERIC	GENITOP	GENUSION	GIANTEC
GIGADEVICE	GMT	GOAL	GOULD
GREEN-ENGINE	GREENLIANT	GREENWICH	GTM
HAIER	HARRIS	HITACHI	HITRENDTECH
HOLTEK	HONEYWELL	HONGKONG	HOPEFIND
HUAJIE Technology		HUAWEI	HYNITRON
HYNIX	HYNIX (HYUNDAI)	HYNIX-CUSTOMER	HYUNDAI
IC Microsystems	ICE	ICMIC	ICSI
ICT	IDT	IK Semiconductor	ILITEK
IML	IMT	INFINEON	INTEGRAL
INTEL	INTELSIL	INTERSIL	IR
ISSI	K-LINE	KODENSHI	LATTICE
LG Semicon	LINEAR	LINKSMART	LITAO



LIZE	LUMINARY	LYONTEK	MACRONIX
MAGNACHIP	MAXCOM	MAXIM	MAXWELL
MEGAWIN	MEMOCOM	MICON	MICROCHIP
MICROCHIP (SST)	MICRON	MICRONAS	MICRON-CUSTOMER
MIP	MIRA	MITSUBISHI	MITSUBISHI
MOSEL-VITELIC	MOSMIC	MOSTEK	MOTOROLA
MShine	MT	MXIC	MY-MS
MYSON	NANSI	NANTRONICS	NATRONICS
NEC	NEXFLASH	NJRC	NORDIC
NOVATEK	NSC	NTE	NUMONYX
NUVOTON	NXP	OKI	ON Semiconductor
PANASONIC	PARALLAX	PCT	PHILIPS
PJ	PMC	PORTEK	POWERFLASH
POWER-RAIL	PSS	PTC	QISDA-CUSTOMER
QIXIN	Quick Pulse	RAMTRON	RATO
RAYDIUM	REALTEK	RENESAS	RICHTEK
RICOH	ROCKWELL	ROHM	SAIFUN
SAMSUNG	SAMSUNG-CUSTOMER	SANYO	SCENIX
SEEQ	SEIKO	SGS-THOMSON	SHARP
SHENHUI	SIEMENS	SIERRA	SIGNETICS
Silicon Laboratories		SILICON7	SIMTEK
SINOWEALTH	SIRF	SMI	SMOS
SONIX	SONY	SPACE ELECTRONICS[Sei]	
SPANSION	SSSC	SST	SST-CUSTOMER
SSU	ST	STC	ST-CUSTOMER
SULC	SUMMIT	SUNMOON	SUNPLUS
SYNCMOS	SYNERTEK	SYNTEK	SZXG
TECHCODE	TEKMOS	TEMIC	TERIDIAN
Terra Semiconductor		TI	TI-CUSTOMER
TMC	TOSHIBA	TOSHIBA-CUSTOMER	TURBO IC
UBICOM	UMC	UNIGEN	VANTIS
VERSACHIPS	VLSI	WELTREND	
WHITE ELECTRONIC DESIGNS		WINBOND	WING Shing
WSI	XELTEK	XICOR	XILINX
XINNOVA	XINYANG	XUMARS	YMC
YSS	YXLDZ	ZENTEL	ZHENGXIN
ZILOG	ZMD		

## ABOV

### MICROCONTROLLER

GMS34004TK [CX0001]	GMS34004TM [CX0001]
GMS34004TW [CX0001]	GMS34112TK [CX0001]
GMS34112TK@SOIC20 [CX1033]	GMS34112TK@SSOP20 [CX1026]
GMS34140TK [CX0001]	GMS34140TK@SOIC24 [CX1033]
GMS80C701 [CX0001]	GMS80C701@PLCC44 [CX2044]
GMS80C701@TQFP44 [CX3002]	GMS81004(dip20) [CX0001]
GMS81004(dip24) [CX0001]	GMS81004(dip28) [CX0001]
GMS81004@PLCC44 [CX2044]	GMS81004@SOIC20 [CX1033]
GMS81004@SOIC24 [CX1033]	GMS81004@SOIC28 [CX1033]
GMS81008(dip20) [CX0001]	GMS81008(dip24) [CX0001]
GMS81008(dip28) [CX0001]	GMS81008@PLCC44 [CX2044]

GMS81008@SOIC20 [CX1033]  
GMS81008@SOIC28 [CX1033]  
GMS81016(dip24) [CX0001]  
GMS81016@PLCC44 [CX2044]  
GMS81016@SOIC24 [CX1033]  
GMS81024(dip20) [CX0001]  
GMS81024(dip28) [CX0001]  
GMS81024@SOIC20 [CX1033]  
GMS81024@SOIC28 [CX1033]  
GMS81032(dip24) [CX0001]  
GMS81032@PLCC44 [CX2044]  
GMS81032@SOIC24 [CX1033]  
GMS81504AT [CX0032]  
GMS81516 [CX0001]  
GMS81516@MQFP64 [CX3015]  
GMS81516AT [CX0001]  
GMS81516AT@MQFP64 [CX3015]  
GMS81516BT [CX0001]  
GMS81516BT@MQFP64 [CX3015]  
GMS81524 [CX0001]  
GMS81524@MQFP64 [CX3015]  
GMS81524AT [CX0001]  
GMS81524AT@MQFP64 [CX3015]  
GMS81524BT [CX0001]  
GMS81524BT@MQFP64 [CX3015]  
GMS81604T [CX0001]  
GMS81604T@SDIP42 [CX0042]  
GMS81608T@PLCC44 [CX2044]  
GMS81C5016(dip28) [CX0001]  
GMS81C5016@PLCC44 [CX2044]  
GMS81C5016@TQFP44 [CX3002]  
GMS81C5024(dip40) [CX0001]  
GMS81C5024@SOIC28 [CX1033]  
GMS81C5032(dip28) [CX0001]  
GMS81C5032@PLCC44 [CX2044]  
GMS81C5032@TQFP44 [CX3002]  
GMS82516T@LQFP64 [CX3011]  
GMS82516T@MQFP64 [CX3015]  
GMS82516T@SDIP64 [CX0064]  
GMS82524T@LQFP64 [CX3011]  
GMS82524T@MQFP64 [CX3015]  
GMS82524T@SDIP64 [CX0064]  
GMS84524T@SDIP52 [CX0056]  
GMS87C1102@SOP16 [CX1033]  
GMS87C1202@SOP20 [CX1033]  
GMS87C1404@SOP28 [CX1033]  
GMS87C1408@SOP28 [CX1033]  
GMS87C2020@MQFP64 [CX3015]  
GMS87C5032(dip28) [CX0001]  
GMS87C5032@PLCC44 [CX2044]  
GMS87C5032@TQFP44 [CX3002]  
GMS87C7008@LQFP64 [CX3011]  
GMS87C7008@SDIP64 [CX0064]  
GMS87C7016@MQFP64 [CX3015]  
GMS97C1051 [CX0001]  
GMS97C2051 [CX0001]  
GMS97C51 [CX0001]  
GMS97C51@TQFP44 [CX3002]  
GMS97C51H@PLCC44 [CX2044]

GMS81008@SOIC24 [CX1033]  
GMS81016(dip20) [CX0001]  
GMS81016(dip28) [CX0001]  
GMS81016@SOIC20 [CX1033]  
GMS81016@SOIC28 [CX1033]  
GMS81024(dip24) [CX0001]  
GMS81024@PLCC44 [CX2044]  
GMS81024@SOIC24 [CX1033]  
GMS81032(dip20) [CX0001]  
GMS81032(dip28) [CX0001]  
GMS81032@SOIC20 [CX1033]  
GMS81032@SOIC28 [CX1033]  
GMS81504T [CX0032]  
GMS81516@LQFP64 [CX3011]  
GMS81516@SDIP64 [CX0064]  
GMS81516AT@LQFP64 [CX3011]  
GMS81516AT@SDIP64 [CX0064]  
GMS81516BT@LQFP64 [CX3011]  
GMS81516BT@SDIP64 [CX0064]  
GMS81524@LQFP64 [CX3011]  
GMS81524@SDIP64 [CX0064]  
GMS81524AT@LQFP64 [CX3011]  
GMS81524AT@SDIP64 [CX0064]  
GMS81524BT@LQFP64 [CX3011]  
GMS81524BT@SDIP64 [CX0064]  
GMS81604T@PLCC44 [CX2044]  
GMS81608T [CX0001]  
GMS81608T@SDIP42 [CX0042]  
GMS81C5016(dip40) [CX0001]  
GMS81C5016@SOIC28 [CX1033]  
GMS81C5024(dip28) [CX0001]  
GMS81C5024@PLCC44 [CX2044]  
GMS81C5024@TQFP44 [CX3002]  
GMS81C5032(dip40) [CX0001]  
GMS81C5032@SOIC28 [CX1033]  
GMS82516T [CX0001]  
GMS82516T@MQFP44 [CX3002]  
GMS82516T@SDIP42 [CX0042]  
GMS82524T [CX0001]  
GMS82524T@MQFP44 [CX3002]  
GMS82524T@SDIP42 [CX0042]  
GMS84512T@SDIP52 [CX0056]  
GMS87C1102 [CX0001]  
GMS87C1202 [CX0001]  
GMS87C1404 [CX0001]  
GMS87C1408 [CX0001]  
GMS87C2020@LQFP64 [CX3011]  
GMS87C2020@SDIP64 [CX0064]  
GMS87C5032(dip40) [CX0001]  
GMS87C5032@SOIC28 [CX1033]  
GMS87C5108@PQFP80 [CX3019]  
GMS87C7008@MQFP64 [CX3015]  
GMS87C7016@LQFP64 [CX3011]  
GMS87C7016@SDIP64 [CX0064]  
GMS97C1051@SOIC20 [CX1033]  
GMS97C2051@SOIC20 [CX1033]  
GMS97C51@PLCC44 [CX2044]  
GMS97C51H [CX0001]  
GMS97C51H@TQFP44 [CX3002]

GMS97C52 [CX0001]  
GMS97C52@TQFP44 [CX3002]  
GMS97C52H@PLCC44 [CX2044]  
GMS97C54 [CX0001]  
GMS97C54@TQFP44 [CX3002]  
GMS97C54H@PLCC44 [CX2044]  
GMS97C56 [CX0001]  
GMS97C56@TQFP44 [CX3002]  
GMS97C56H@PLCC44 [CX2044]  
GMS97C58 [CX0001]  
GMS97C58@TQFP44 [CX3002]  
GMS97C58H@PLCC44 [CX2044]  
GMS97L1051 [CX0001]  
GMS97L2051 [CX0001]  
GMS97L51 [CX0001]  
GMS97L51@TQFP44 [CX3002]  
GMS97L52@PLCC44 [CX2044]  
GMS97L54 [CX0001]  
GMS97L54@TQFP44 [CX3002]  
GMS97L56@PLCC44 [CX2044]  
GMS97L58 [CX0001]  
GMS97L58@TQFP44 [CX3002]  
GMS99C51@PLCC44 [CX2044]  
GMS99C52 [CX0001]  
GMS99C52@TQFP44 [CX3002]  
GMS99C58@PLCC44 [CX2044]  
HMS81004E(dip20) [CX0001]  
HMS81004E(dip28) [CX0001]  
HMS81004E@SOIC20 [CX1033]  
HMS81004E@SOIC28 [CX1033]  
HMS81008E(dip24) [CX0001]  
HMS81008E@PLCC44 [CX2044]  
HMS81008E@SOIC24 [CX1033]  
HMS81016E(dip20) [CX0001]  
HMS81016E(dip28) [CX0001]  
HMS81016E@SOIC20 [CX1033]  
HMS81016E@SOIC28 [CX1033]  
HMS81020ET(dip24) [CX0001]  
HMS81020ET@SOIC20 [CX1033]  
HMS81020ET@SOIC28 [CX1033]  
HMS81020TL(dip24) [CX0001]  
HMS81020TL@SOIC20 [CX1033]  
HMS81020TL@SOIC28 [CX1033]  
HMS81024E(dip24) [CX0001]  
HMS81024E@PLCC44 [CX2044]  
HMS81024E@SOIC24 [CX1033]  
HMS81032(dip20) [CX0001]  
HMS81032(dip28) [CX0001]  
HMS81032@SOIC24 [CX1033]  
HMS81032ET(dip20) [CX0001]  
HMS81032ET(dip28) [CX0001]  
HMS81032ET@SOIC24 [CX1033]  
HMS81032T(dip20) [CX0001]  
HMS81032T(dip28) [CX0001]  
HMS81032T@SOIC24 [CX1033]  
HMS81032TL(dip20) [CX0001]  
HMS81032TL(dip28) [CX0001]  
HMS81032TL@SOIC24 [CX1033]  
HMS87C1102A [CX0001]

GMS97C52@PLCC44 [CX2044]  
GMS97C52H [CX0001]  
GMS97C52H@TQFP44 [CX3002]  
GMS97C54@PLCC44 [CX2044]  
GMS97C54H [CX0001]  
GMS97C54H@TQFP44 [CX3002]  
GMS97C56@PLCC44 [CX2044]  
GMS97C56H [CX0001]  
GMS97C56H@TQFP44 [CX3002]  
GMS97C58@PLCC44 [CX2044]  
GMS97C58H [CX0001]  
GMS97C58H@TQFP44 [CX3002]  
GMS97L1051@SOIC20 [CX1033]  
GMS97L2051@SOIC20 [CX1033]  
GMS97L51@PLCC44 [CX2044]  
GMS97L52 [CX0001]  
GMS97L52@TQFP44 [CX3002]  
GMS97L54@PLCC44 [CX2044]  
GMS97L56 [CX0001]  
GMS97L56@TQFP44 [CX3002]  
GMS97L58@PLCC44 [CX2044]  
GMS99C51 [CX0001]  
GMS99C51@TQFP44 [CX3002]  
GMS99C52@PLCC44 [CX2044]  
GMS99C58 [CX0001]  
GMS99C58@TQFP44 [CX3002]  
HMS81004E(dip24) [CX0001]  
HMS81004E@PLCC44 [CX2044]  
HMS81004E@SOIC24 [CX1033]  
HMS81008E(dip20) [CX0001]  
HMS81008E(dip28) [CX0001]  
HMS81008E@SOIC20 [CX1033]  
HMS81008E@SOIC28 [CX1033]  
HMS81016E(dip24) [CX0001]  
HMS81016E@PLCC44 [CX2044]  
HMS81016E@SOIC24 [CX1033]  
HMS81020ET(dip20) [CX0001]  
HMS81020ET(dip28) [CX0001]  
HMS81020ET@SOIC24 [CX1033]  
HMS81020TL(dip20) [CX0001]  
HMS81020TL(dip28) [CX0001]  
HMS81020TL@SOIC24 [CX1033]  
HMS81024E(dip20) [CX0001]  
HMS81024E(dip28) [CX0001]  
HMS81024E@SOIC20 [CX1033]  
HMS81024E@SOIC28 [CX1033]  
HMS81032(dip24) [CX0001]  
HMS81032@SOIC20 [CX1033]  
HMS81032@SOIC28 [CX1033]  
HMS81032ET(dip24) [CX0001]  
HMS81032ET@SOIC20 [CX1033]  
HMS81032ET@SOIC28 [CX1033]  
HMS81032T(dip24) [CX0001]  
HMS81032T@SOIC20 [CX1033]  
HMS81032T@SOIC28 [CX1033]  
HMS81032TL(dip24) [CX0001]  
HMS81032TL@SOIC20 [CX1033]  
HMS81032TL@SOIC28 [CX1033]  
HMS87C1102A@SOP16 [CX1033]

HMS87C1104A [CX0001] HMS87C1104A@SOP16 [CX1033]  
HMS87C1202A [CX0001] HMS87C1202A@SOP20 [CX1033]  
HMS87C1204A [CX0001] HMS87C1204A@SOP20 [CX1033]  
HMS87C1302A@SDIP24 [CX0032] HMS87C1302A@SOP24 [CX1033]  
HMS87C1304A@SDIP24 [CX0032] HMS87C1304A@SOP24 [CX1033]  
HMS87C1404B [CX0001] HMS87C1404B@SDIP28 [CX0032]  
HMS87C1404B@SOIC28 [CX1033] HMS87C1408B [CX0001]  
HMS87C1408B@SDIP28 [CX0032] HMS87C1408B@SOIC28 [CX1033]  
HMS87C1416B [CX0001] HMS87C1416B@SDIP28 [CX0032]  
HMS87C1416B@SOIC28 [CX1033] HMS87C1508B [CX0001]  
HMS87C1516B [CX0001] HMS87C1608B [CX0001]  
HMS87C1616B [CX0001] HMS87C1708B@SDIP42 [CX0042]  
HMS87C1716B@SDIP42 [CX0042] HMS87C1808B@TQFP44 [CX3002]  
HMS87C1816B@TQFP44 [CX3002] HMS87C5216 [CX0001]  
HMS87C5216@PLCC44 [CX2044] HMS87C5216@SOIC28 [CX1033]  
HMS87C5216@TQFP44 [CX3002] HMS99C51 [CX0001]  
HMS99C51@PLCC44 [CX2044] HMS99C51@TQFP44 [CX3002]  
HMS99C52 [CX0001] HMS99C52@PLCC44 [CX2044]  
HMS99C52@TQFP44 [CX3002] HMS99C58 [CX0001]  
HMS99C58@PLCC44 [CX2044] HMS99C58@TQFP44 [CX3002]  
MC40P5001D@SOP20 [CX1033] MC40P5004BD@SOP20(1K) [CX1033]  
MC40P5004BD@SOP20(2K) [CX1033] MC40P5004BD@SOP20(4K) [CX1033]  
MC40P5004BR@TSSOP20(1K) [CX1067] MC40P5004BR@TSSOP20(2K) [CX1067]  
MC40P5004BR@TSSOP20(4K) [CX1067] MC40P5101D@SOP20 [CX1033]  
MC40P5104BM@SOP16(1K) [CX1016] MC40P5104BM@SOP16(2K) [CX1016]  
MC40P5104BM@SOP16(4K) [CX1016] MC40P5201D@SOP24 [CX1033]  
MC40P5204BD@SOP24(1K) [CX1033] MC40P5204BD@SOP24(2K) [CX1033]  
MC40P5204BD@SOP24(4K) [CX1033] MC40P5301D@SOP24 [CX1033]  
MC40P5404BD@SOP20(1K) [CX1033] MC40P5404BD@SOP20(2K) [CX1033]  
MC40P5404BD@SOP20(4K) [CX1033] MC40P6004BD@SOP20(1K) [CX1033]  
MC40P6004BD@SOP20(2K) [CX1033] MC40P6004BD@SOP20(4K) [CX1033]  
MC40P6004BR@TSSOP20(1K) [CX1067] MC40P6004BR@TSSOP20(2K) [CX1067]  
MC40P6004BR@TSSOP20(4K) [CX1067] MC40P6104M@SOP16(1K) [CX1016]  
MC40P6104M@SOP16(2K) [CX1016] MC40P6104M@SOP16(4K) [CX1016]  
MC80F0104 [CX0001] MC80F0104@SOP16 [CX1033]  
MC80F0104@TSSOP16 [CX1033] MC80F0204 [CX0001]  
MC80F0204@SOP20 [CX1033] MC80F0208K@SDIP42 [CX0042]  
MC80F0208Q@MQFP44 [CX3002] MC80F0216K@SDIP42 [CX0042]  
MC80F0216Q@MQFP44 [CX3002] MC80F0224K@SDIP42 [CX0042]  
MC80F0224Q@MQFP44 [CX3002] MC80F0304 [CX0001]  
MC80F0304@SOP28 [CX1033] MC80F0308 [CX0001]  
MC80F0308@SOP28 [CX1033] MC80F0316 [CX0001]  
MC80F0316@SOP28 [CX1033] MC80F0424K@SDIP64 [CX0064]  
MC80F0424L@LQFP64 [CX3011] MC80F0424Q@MQFP64 [CX3015]  
MC80F0432K@SDIP64 [CX0064] MC80F0432L@LQFP64 [CX3011]  
MC80F0432Q@MQFP64 [CX3015] MC80F0448K@SDIP64 [CX0064]  
MC80F0448L@LQFP64 [CX3011] MC80F0448Q@MQFP64 [CX3015]  
MC80F0504 [CX0001] MC80F0504@SOP16 [CX1036]  
MC80F0504@SSOP16 [CX1026] MC80F0504[153mil]@SOP16 [CX1030]  
MC80F0604 [CX0001] MC80F0604@SOP20 [CX1036]  
MC80F0604@SSOP20 [CX1026] MC80F0704 [CX0001]  
MC80F0704@QFN28 [CX0001] MC80F0704@SOP28 [CX1036]  
MC80F0708 [CX0001] MC80F0708@QFN28 [CX0001]  
MC80F0708@SOP28 [CX1036] MC80F0804@SDIP32 [CX0032]  
MC80F0804@SOP32 [CX1069] MC80F0808@SDIP32 [CX0032]  
MC80F0808@SOP32 [CX1069] MC80F7108@LQFP44 [CX3003]  
MC80F7108@MQFP44 [CX3002] MC80F7208@SDIP42 [CX0042]  
MC80F7308@LQFP64 [CX3011] MC80F7308@MQFP64 [CX3015]  
MC80F7408@LQFP44 [CX3003] MC80F7408@MQFP44 [CX3002]

MC81F4104B [CX0001]  
MC81F4104S@SSOP10 [CX1076]  
MC81F4204D@SOP20 [CX1033]  
MC81F4204R@TSSOP16 [CX1000]  
MC81F4204W@TSSOP20 [CX1000]  
MC81F4215D@SOP20 [CX1033]  
MC81F4216D@SOP20 [CX1033]  
MC81F4315G [CX0001]  
MC81F4315L@LQFP32 [CX3001]  
MC81F4315S@SSOP24 [CX1000]  
MC81F4316G [CX0001]  
MC81F4316M@SOP28 [CX1033]  
MC81F4416K@SDIP42 [CX0042]  
MC96F6332D@SOP32 [CX1069-1]  
MC96F6332M@SOP28 [CX1033-7]  
MC96F7816L@QFP80 [CX3016-2]

MC81F4104M@SOP8 [CX1045]  
MC81F4204B [CX0001]  
MC81F4204M@SOP16 [CX1033]  
MC81F4204V [CX0001]  
MC81F4215B [CX0001]  
MC81F4216B [CX0001]  
MC81F4315D@SOP32 [CX1069]  
MC81F4315K@SDIP32 [CX0032]  
MC81F4315M@SOP28 [CX1033]  
MC81F4316D@SOP32 [CX1069]  
MC81F4316K@SDIP32 [CX0032]  
MC81F4316S@SSOP24 [CX1000]  
MC81F4416Q@MQFP44 [CX3046]  
MC96F6332L@QFP32 [CX3001-2]  
MC96F6432Q@QFP44 [CX3002-1]  
MC96F7816Q@QFP80 [CX3019-1]

## ACE Technology

### E (E) PROM/FRAM/NVRAM

ACE24C02A [CX0001]  
ACE24C02A@TSSOP8 [CX1059]  
ACE24C04A@SOIC8 [CX1045]  
ACE24C08A [CX0001]  
ACE24C08A@TSSOP8 [CX1059]  
ACE24C128@SOIC8 [CX1045]  
ACE24C16A [CX0001]  
ACE24C16A@TSSOP8 [CX1059]  
ACE24C256@SOIC8 [CX1045]  
ACE24C32 [CX0001]  
ACE24C32@TSSOP8 [CX1059]  
ACE24C64@SOIC8 [CX1045]  
ACE24LC02 [CX0001]  
ACE24LC02@TSSOP8 [CX1059]  
ACE24LC04@SOIC8 [CX1045]  
ACE24LC08 [CX0001]  
ACE24LC08@TSSOP8 [CX1059]  
ACE24LC16@SOIC8 [CX1045]  
ACE93C46(08bit) [CX0001]  
ACE93C46(08bit)@TSSOP8 [CX1059]  
ACE93C46(16bit)@SOIC8 [CX1045]

ACE24C02A@SOIC8 [CX1045]  
ACE24C04A [CX0001]  
ACE24C04A@TSSOP8 [CX1059]  
ACE24C08A@SOIC8 [CX1045]  
ACE24C128 [CX0001]  
ACE24C128@TSSOP8 [CX1059]  
ACE24C16A@SOIC8 [CX1045]  
ACE24C256 [CX0001]  
ACE24C256@TSSOP8 [CX1059]  
ACE24C32@SOIC8 [CX1045]  
ACE24C64 [CX0001]  
ACE24C64@TSSOP8 [CX1059]  
ACE24LC02@SOIC8 [CX1045]  
ACE24LC04 [CX0001]  
ACE24LC04@TSSOP8 [CX1059]  
ACE24LC08@SOIC8 [CX1045]  
ACE24LC16 [CX0001]  
ACE24LC16@TSSOP8 [CX1059]  
ACE93C46(08bit)@SOIC8 [CX1045]  
ACE93C46(16bit) [CX0001]  
ACE93C46(16bit)@TSSOP8 [CX1059]

## ACT

### E (E) PROM/FRAM/NVRAM

93LC46(08bit) [CX0001]  
93LC46(16bit) [CX0001]  
93LC56(08bit) [CX0001]  
93LC56(16bit) [CX0001]  
93LC66(08bit) [CX0001]  
93LC66(16bit) [CX0001]  
93LC86(08bit) [CX0001]  
93LC86(16bit) [CX0001]

93LC46(08bit)@SOIC8 [CX1045]  
93LC46(16bit)@SOIC8 [CX1045]  
93LC56(08bit)@SOIC8 [CX1045]  
93LC56(16bit)@SOIC8 [CX1045]  
93LC66(08bit)@SOIC8 [CX1045]  
93LC66(16bit)@SOIC8 [CX1045]  
93LC86(08bit)@SOIC8 [CX1045]  
93LC86(16bit)@SOIC8 [CX1045]

# ACTRANS

## E ( E ) PROM / FRAM / NVRAM

AC25010@SOIC8 [CX1045#1]	AC25512@SOIC8 [CX1045#1]
AC25LC010@SOIC8 [CX1045#1]	AC25LC512@SOIC8 [CX1045#1]
AC39LV010@FBGA48 [CX5002]	AC39LV010@PLCC32 [CX2032]
AC39LV010@VSOP32 [CX1003]	AC39LV020@FBGA48 [CX5002]
AC39LV020@PLCC32 [CX2032]	AC39LV020@VSOP32 [CX1003]
AC39LV040@PLCC32 [CX2032]	AC39LV040@VSOP32 [CX1003]
AC39LV080@FBGA48 [CX5002]	AC39LV080@TSOP40 [CX1006]
AC39LV088@TSOP48 [CX1004]	AC39LV512@PLCC32 [CX2032]
AC39LV512@VSOP32 [CX1003]	AC39LV800@FBGA48 [CX5002]
AC39LV800@TSOP48 [CX1004]	AC39VF800@FBGA48 [CX5002]
AC39VF800@TSOP48 [CX1004]	

# ADESTO

## E ( E ) PROM / FRAM / NVRAM

AT45DB041E (page256)@MLF8 [CX4005#2]  
AT45DB041E (page256)@SOIC8 [150] [CX1016#1]  
AT45DB041E (page256)@SOIC8 [200] [CX1031#1]  
AT45DB041E (page264)@MLF8 [CX4005-2]  
AT45DB041E (page264)@SOIC8 [150] [CX1016-1]  
AT45DB041E (page264)@SOIC8 [200] [CX1031-1]

# ADI

## MICROCONTROLLER

AD5251@TSSOP14 [CX1001]	AD5252@TSSOP14 [CX1001]
AD5253@TSSOP20 [CX1001]	AD5254@TSSOP20 [CX1001]
ADE5166@LQFP64 [CX3011]	ADE5169@LQFP64 [CX3011]
ADE5566@LQFP64 [CX3011]	ADE5569@LQFP64 [CX3011]
ADUC812BCP@LFCSP56 [CX4022]	ADUC812BS@MQFP52 [CX3009]
ADuC814@SSOP28 [CX1001]	ADUC816@LFCSP56 [CX4022]
ADUC816@MQFP52 [CX3009]	ADUC824@LFCSP56 [CX4022]
ADUC824@MQFP52 [CX3009]	ADuC831BCP@LFCSP56 [CX4022]
ADuC831BS@MQFP52 [CX3009]	ADuC832BCP@LFCSP56 [CX4022]
ADuC832BS@MQFP52 [CX3009]	ADuC834BCP@LFCSP56 [CX4022]
ADuC834BS@MQFP52 [CX3009]	ADuC836BCP@LFCSP56 [CX4022]
ADuC836BS@MQFP52 [CX3009]	ADuC841BCP62@LFCSP56 [CX4022]
ADuC841BCP8@LFCSP56 [CX4022]	ADuC841BS62@MQFP52 [CX3009]
ADuC842BCP32@LFCSP56 [CX4022]	ADuC842BCP62@LFCSP56 [CX4022]
ADuC842BCP8@LFCSP56 [CX4022]	ADuC842BS62@MQFP52 [CX3009]
ADuC843BCP32@LFCSP56 [CX4022]	ADuC843BCP62@LFCSP56 [CX4022]
ADuC843BCP8@LFCSP56 [CX4022]	ADuC843BS62@MQFP52 [CX3009]
ADuC845BCP62@LFCSP56 [CX4022]	ADuC845BCP8@LFCSP56 [CX4022]
ADuC845BS62@MQFP52 [CX3009]	ADuC845BS8@MQFP52 [CX3009]
ADuC847BCP62@LFCSP56 [CX4022]	ADuC847BCP8@LFCSP56 [CX4022]
ADuC847BS32@MQFP52 [CX3009]	ADuC847BS62@MQFP52 [CX3009]
ADuC847BS8@MQFP52 [CX3009]	ADuC848BCP62@LFCSP56 [CX4022]
ADuC848BCP8@LFCSP56 [CX4022]	ADuC848BS32@MQFP52 [CX3009]
ADuC848BS62@MQFP52 [CX3009]	ADuC848BS8@MQFP52 [CX3009]
ADuCM360@LFCSP48 [CX4021]	ADuCM361@LFCSP48 [CX4021]



# ADVANCE GROUP

## E (E) PROM/FRAM/NVRAM

AF24BC01 [CX0001]	AF24BC01@SOIC8 [CX1045]
AF24BC01@TSOP8 [CX1059]	AF24BC02 [CX0001]
AF24BC02@SOIC8 [CX1045]	AF24BC02@TSOP8 [CX1059]
AF24BC04 [CX0001]	AF24BC04@SOIC8 [CX1045]
AF24BC04@TSOP8 [CX1059]	AF24BC08 [CX0001]
AF24BC08@SOIC8 [CX1045]	AF24BC08@TSOP8 [CX1059]
AF24BC16 [CX0001]	AF24BC16@SOIC8 [CX1045]
AF24BC16@TSOP8 [CX1059]	AF24C128 [CX0001]
AF24C128@SOIC8 [CX1045]	AF24C128@TSOP8 [CX1059]
AF24C256 [CX0001]	AF24C256@SOIC8 [CX1045]
AF24C256@TSOP8 [CX1059]	AF24C32 [CX0001]
AF24C32@SOIC8 [CX1045]	AF24C32@TSOP8 [CX1059]
AF24C64 [CX0001]	AF24C64@SOIC8 [CX1045]
AF24C64@TSOP8 [CX1059]	AF93C46(08bit) [CX0001]
AF93C46(08bit)@SOIC8 [CX1045]	AF93C46(08bit)@TSOP8 [CX1059]
AF93C46(16bit) [CX0001]	AF93C46(16bit)@SOIC8 [CX1045]
AF93C46(16bit)@TSOP8 [CX1059]	AF93C56(08bit) [CX0001]
AF93C56(08bit)@SOIC8 [CX1045]	AF93C56(08bit)@TSOP8 [CX1059]
AF93C56(16bit) [CX0001]	AF93C56(16bit)@SOIC8 [CX1045]
AF93C56(16bit)@TSOP8 [CX1059]	AF93C66(08bit) [CX0001]
AF93C66(08bit)@SOIC8 [CX1045]	AF93C66(08bit)@TSOP8 [CX1059]
AF93C66(16bit) [CX0001]	AF93C66(16bit)@SOIC8 [CX1045]
AF93C66(16bit)@TSOP8 [CX1059]	AF93C86(08bit) [CX0001]
AF93C86(08bit)@SOIC8 [CX1045]	AF93C86(08bit)@TSOP8 [CX1059]
AF93C86(16bit) [CX0001]	AF93C86(16bit)@SOIC8 [CX1045]
AF93C86(16bit)@TSOP8 [CX1059]	

## MICROCONTROLLER

AG89P51	AG89P51@PLCC44
AG89P51@PQFP44	AG89P51A
AG89P51A@PLCC44	AG89P51A@PQFP44
AG89P52	AG89P52@PLCC44
AG89P52@PQFP44	

# AiT Semiconductor

## E (E) PROM/FRAM/NVRAM

A24C02 [CX0001]	A24C02@SOP8 [CX1045]
A24C02@SOT23-5 [CX1041]	A24C02@TSSOP8 [CX1059]
A24C04 [CX0001]	A24C04@SOP8 [CX1045]
A24C04@SOT23-5 [CX1041]	A24C04@TSSOP8 [CX1059]
A24C08 [CX0001]	A24C08@SOP8 [CX1045]
A24C08@SOT23-5 [CX1041]	A24C08@TSSOP8 [CX1059]
A24C128@SOP8 [CX1045]	A24C128@TSSOP8 [CX1059]
A24C16 [CX0001]	A24C16@SOP8 [CX1045]
A24C16@SOT23-5 [CX1041]	A24C16@TSSOP8 [CX1059]
A24C256@SOP8 [CX1045]	A24C256@TSSOP8 [CX1059]
A24C32@DFN8 [CX4002]	A24C32@SOP8 [CX1045]
A24C32@TSSOP8 [CX1059]	A24C64@SOP8 [CX1045]
A24C64@TSSOP8 [CX1059]	A93C46(08bit)@SOP8 [CX1045]

A93C46(08bit)@TSSOP8 [CX1059]  
A93C46(16bit)@TSSOP8 [CX1059]  
A93C56(08bit)@TSSOP8 [CX1059]  
A93C56(16bit)@TSSOP8 [CX1059]  
A93C66(08bit)@TSSOP8 [CX1059]  
A93C66(16bit)@TSSOP8 [CX1059]

A93C46(16bit)@SOP8 [CX1045]  
A93C56(08bit)@SOP8 [CX1045]  
A93C56(16bit)@SOP8 [CX1045]  
A93C66(08bit)@SOP8 [CX1045]  
A93C66(16bit)@SOP8 [CX1045]

## ALI(Acer)

### E (E) PROM/FRAM/NVRAM

M8720 [CX0001]

M8720@PLCC32 [CX2032]

### MICROCONTROLLER

M6759 [CX0001]  
M6759@TQFP44 [CX3002]

M6759@PLCC44 [CX2044]

## ALL24SERIES

### E (E) PROM/FRAM/NVRAM

24C01(ISP) [CX0001]  
24C04(ISP) [CX0001]  
24C128(ISP) [CX0001]  
24C256(ISP) [CX0001]  
24C64(ISP) [CX0001]

24C02(ISP) [CX0001]  
24C08(ISP) [CX0001]  
24C16(ISP) [CX0001]  
24C32(ISP) [CX0001]

## ALLFLASH

### E (E) PROM/FRAM/NVRAM

AFA1G08T@TSOP48 [CX1004-3]

## ALLIANCE

### E (E) PROM/FRAM/NVRAM

AS29F200B@PSOP44 [CX1014]  
AS29F200T@PSOP44 [CX1014]  
AS29LV160B@TSOP48 [CX1004]  
AS29LV400B@TSOP48 [CX1004]  
AS29LV800B@TSOP48 [CX1004]

AS29F200B@TSOP48 [CX1004]  
AS29F200T@TSOP48 [CX1004]  
AS29LV160T@TSOP48 [CX1004]  
AS29LV400T@TSOP48 [CX1004]  
AS29LV800T@TSOP48 [CX1004]

## ALTCO

### MICROCONTROLLER

ST72F321AR6T3 [CX3011]  
ST72F321AR6TA [CX3011]  
ST72F321AR7T6 [CX3011]  
ST72F321AR9T3 [CX3011]  
ST72F321AR9TA [CX3011]

ST72F321AR6T6 [CX3011]  
ST72F321AR7T3 [CX3011]  
ST72F321AR7TA [CX3011]  
ST72F321AR9T6 [CX3011]  
ST72F321AR9TC [CX3011]

ST72F321BAR6T3 [CX3011]  
ST72F321BAR6TA [CX3011]  
ST72F321BAR7T6 [CX3011]  
ST72F321BAR9T3 [CX3011]  
ST72F321BAR9TA [CX3011]  
ST72F321BJ6T3 [CX3003]  
ST72F321BJ6TA [CX3003]  
ST72F321BJ7T6 [CX3003]  
ST72F321BJ9T3 [CX3003]  
ST72F321BJ9TA [CX3003]  
ST72F321BM9T3 [CX3054]  
ST72F321BM9TC [CX3054]  
ST72F321BR6T6 [CX3013]  
ST72F321BR7T3 [CX3013]  
ST72F321BR7TA [CX3013]  
ST72F321BR9T6 [CX3013]  
ST72F321BR9TC [CX3013]  
ST72F321J6T6 [CX3003]  
ST72F321J7T3 [CX3003]  
ST72F321J7TA [CX3003]  
ST72F321J9T6 [CX3003]  
ST72F321J9TC [CX3003]  
ST72F321M9T6 [CX3054]  
ST72F321R6T3 [CX3013]  
ST72F321R6TA [CX3013]  
ST72F321R7T6 [CX3013]  
ST72F321R9T3 [CX3013]  
ST72F321R9TA [CX3013]  
ST72F324BJ2B3 [CX0042]  
ST72F324BJ2B6 [CX0042]  
ST72F324BJ2BC [CX0042]  
ST72F324BJ2T5 [CX3003]  
ST72F324BJ2TA [CX3003]  
ST72F324BJ4B3 [CX0042]  
ST72F324BJ4B6 [CX0042]  
ST72F324BJ4BC [CX0042]  
ST72F324BJ4T5 [CX3003]  
ST72F324BJ4TA [CX3003]  
ST72F324BJ6B3 [CX0042]  
ST72F324BJ6B6 [CX0042]  
ST72F324BJ6BC [CX0042]  
ST72F324BJ6T5 [CX3003]  
ST72F324BJ6TA [CX3003]  
ST72F324BK2B3 [CX0032]  
ST72F324BK2B6 [CX0032]  
ST72F324BK2BC [CX0032]  
ST72F324BK2T5 [CX3001]  
ST72F324BK2TA [CX3001]  
ST72F324BK4B3 [CX0032]  
ST72F324BK4B6 [CX0032]  
ST72F324BK4BC [CX0032]  
ST72F324BK4T5 [CX3001]  
ST72F324BK4TA [CX3001]  
ST72F324BK6B3 [CX0032]  
ST72F324BK6B6 [CX0032]  
ST72F324BK6BC [CX0032]  
ST72F324BK6T5 [CX3001]  
ST72F324BK6TA [CX3001]  
ST72F324J2B3 [CX0042]

ST72F321BAR6T6 [CX3011]  
ST72F321BAR7T3 [CX3011]  
ST72F321BAR7TA [CX3011]  
ST72F321BAR9T6 [CX3011]  
ST72F321BAR9TC [CX3011]  
ST72F321BJ6T6 [CX3003]  
ST72F321BJ7T3 [CX3003]  
ST72F321BJ7TA [CX3003]  
ST72F321BJ9T6 [CX3003]  
ST72F321BJ9TC [CX3003]  
ST72F321BM9T6 [CX3054]  
ST72F321BR6T3 [CX3013]  
ST72F321BR6TA [CX3013]  
ST72F321BR7T6 [CX3013]  
ST72F321BR9T3 [CX3013]  
ST72F321BR9TA [CX3013]  
ST72F321J6T3 [CX3003]  
ST72F321J6TA [CX3003]  
ST72F321J7T6 [CX3003]  
ST72F321J9T3 [CX3003]  
ST72F321J9TA [CX3003]  
ST72F321M9T3 [CX3054]  
ST72F321M9TC [CX3054]  
ST72F321R6T6 [CX3013]  
ST72F321R7T3 [CX3013]  
ST72F321R7TA [CX3013]  
ST72F321R9T6 [CX3013]  
ST72F321R9TC [CX3013]  
ST72F324BJ2B5 [CX0042]  
ST72F324BJ2BA [CX0042]  
ST72F324BJ2T3 [CX3003]  
ST72F324BJ2T6 [CX3003]  
ST72F324BJ2TC [CX3003]  
ST72F324BJ4B5 [CX0042]  
ST72F324BJ4BA [CX0042]  
ST72F324BJ4T3 [CX3003]  
ST72F324BJ4T6 [CX3003]  
ST72F324BJ4TC [CX3003]  
ST72F324BJ6B5 [CX0042]  
ST72F324BJ6BA [CX0042]  
ST72F324BJ6T3 [CX3003]  
ST72F324BJ6T6 [CX3003]  
ST72F324BJ6TC [CX3003]  
ST72F324BK2B5 [CX0032]  
ST72F324BK2BA [CX0032]  
ST72F324BK2T3 [CX3001]  
ST72F324BK2T6 [CX3001]  
ST72F324BK2TC [CX3001]  
ST72F324BK4B5 [CX0032]  
ST72F324BK4BA [CX0032]  
ST72F324BK4T3 [CX3001]  
ST72F324BK4T6 [CX3001]  
ST72F324BK4TC [CX3001]  
ST72F324BK6B5 [CX0032]  
ST72F324BK6BA [CX0032]  
ST72F324BK6T3 [CX3001]  
ST72F324BK6T6 [CX3001]  
ST72F324BK6TC [CX3001]  
ST72F324J2B5 [CX0042]

ST72F324J2B6 [CX0042]  
ST72F324J2BC [CX0042]  
ST72F324J2T5 [CX3003]  
ST72F324J2TA [CX3003]  
ST72F324J4B3 [CX0042]  
ST72F324J4B6 [CX0042]  
ST72F324J4BC [CX0042]  
ST72F324J4T5 [CX3003]  
ST72F324J4TA [CX3003]  
ST72F324J6B3 [CX0042]  
ST72F324J6B6 [CX0042]  
ST72F324J6BC [CX0042]  
ST72F324J6T5 [CX3003]  
ST72F324J6TA [CX3003]  
ST72F324K2B3 [CX0032]  
ST72F324K2B6 [CX0032]  
ST72F324K2BC [CX0032]  
ST72F324K2T5 [CX3001]  
ST72F324K2TA [CX3001]  
ST72F324K4B3 [CX0032]  
ST72F324K4B6 [CX0032]  
ST72F324K4BC [CX0032]  
ST72F324K4T5 [CX3001]  
ST72F324K4TA [CX3001]  
ST72F324K6B3 [CX0032]  
ST72F324K6B6 [CX0032]  
ST72F324K6BC [CX0032]  
ST72F324K6T5 [CX3001]  
ST72F324K6TA [CX3001]  
ST72F324LJ2B3 [CX0042]  
ST72F324LJ2B6 [CX0042]  
ST72F324LJ2BC [CX0042]  
ST72F324LJ2T5 [CX3003]  
ST72F324LJ2TA [CX3003]  
ST72F324LJ4B3 [CX0042]  
ST72F324LJ4B6 [CX0042]  
ST72F324LJ4BC [CX0042]  
ST72F324LJ4T5 [CX3003]  
ST72F324LJ4TA [CX3003]  
ST72F324LJ6B3 [CX0042]  
ST72F324LJ6B6 [CX0042]  
ST72F324LJ6BC [CX0042]  
ST72F324LJ6T5 [CX3003]  
ST72F324LJ6TA [CX3003]  
ST72F324LK2B3 [CX0032]  
ST72F324LK2B6 [CX0032]  
ST72F324LK2BC [CX0032]  
ST72F324LK2T5 [CX3001]  
ST72F324LK2TA [CX3001]  
ST72F324LK4B3 [CX0032]  
ST72F324LK4B6 [CX0032]  
ST72F324LK4BC [CX0032]  
ST72F324LK4T5 [CX3001]  
ST72F324LK4TA [CX3001]  
ST72F324LK6B3 [CX0032]  
ST72F324LK6B6 [CX0032]  
ST72F324LK6BC [CX0032]  
ST72F324LK6T5 [CX3001]  
ST72F324LK6TA [CX3001]

ST72F324J2BA [CX0042]  
ST72F324J2T3 [CX3003]  
ST72F324J2T6 [CX3003]  
ST72F324J2TC [CX3003]  
ST72F324J4B5 [CX0042]  
ST72F324J4BA [CX0042]  
ST72F324J4T3 [CX3003]  
ST72F324J4T6 [CX3003]  
ST72F324J4TC [CX3003]  
ST72F324J6B5 [CX0042]  
ST72F324J6BA [CX0042]  
ST72F324J6T3 [CX3003]  
ST72F324J6T6 [CX3003]  
ST72F324J6TC [CX3003]  
ST72F324K2B5 [CX0032]  
ST72F324K2BA [CX0032]  
ST72F324K2T3 [CX3001]  
ST72F324K2T6 [CX3001]  
ST72F324K2TC [CX3001]  
ST72F324K4B5 [CX0032]  
ST72F324K4BA [CX0032]  
ST72F324K4T3 [CX3001]  
ST72F324K4T6 [CX3001]  
ST72F324K4TC [CX3001]  
ST72F324K6B5 [CX0032]  
ST72F324K6BA [CX0032]  
ST72F324K6T3 [CX3001]  
ST72F324K6T6 [CX3001]  
ST72F324K6TC [CX3001]  
ST72F324LJ2B5 [CX0042]  
ST72F324LJ2BA [CX0042]  
ST72F324LJ2T3 [CX3003]  
ST72F324LJ2T6 [CX3003]  
ST72F324LJ2TC [CX3003]  
ST72F324LJ4B5 [CX0042]  
ST72F324LJ4BA [CX0042]  
ST72F324LJ4T3 [CX3003]  
ST72F324LJ4T6 [CX3003]  
ST72F324LJ4TC [CX3003]  
ST72F324LJ6B5 [CX0042]  
ST72F324LJ6BA [CX0042]  
ST72F324LJ6T3 [CX3003]  
ST72F324LJ6T6 [CX3003]  
ST72F324LJ6TC [CX3003]  
ST72F324LK2B5 [CX0032]  
ST72F324LK2BA [CX0032]  
ST72F324LK2T3 [CX3001]  
ST72F324LK2T6 [CX3001]  
ST72F324LK2TC [CX3001]  
ST72F324LK4B5 [CX0032]  
ST72F324LK4BA [CX0032]  
ST72F324LK4T3 [CX3001]  
ST72F324LK4T6 [CX3001]  
ST72F324LK4TC [CX3001]  
ST72F324LK6B5 [CX0032]  
ST72F324LK6BA [CX0032]  
ST72F324LK6T3 [CX3001]  
ST72F324LK6T6 [CX3001]  
ST72F324LK6TC [CX3001]

ST72F325AR6T3 [CX3011]	ST72F325AR6T5 [CX3011]
ST72F325AR6T6 [CX3011]	ST72F325AR7T3 [CX3011]
ST72F325AR7T5 [CX3011]	ST72F325AR7T6 [CX3011]
ST72F325AR9T3 [CX3011]	ST72F325AR9T5 [CX3011]
ST72F325AR9T6 [CX3011]	ST72F325C4T3 [CX3007]
ST72F325C4T5 [CX3007]	ST72F325C4T6 [CX3007]
ST72F325C6T3 [CX3007]	ST72F325C6T5 [CX3007]
ST72F325C6T6 [CX3007]	ST72F325C7T3 [CX3007]
ST72F325C7T5 [CX3007]	ST72F325C7T6 [CX3007]
ST72F325C9T3 [CX3007]	ST72F325C9T5 [CX3007]
ST72F325C9T6 [CX3007]	ST72F325J4B3 [CX0042]
ST72F325J4B5 [CX0042]	ST72F325J4B6 [CX0042]
ST72F325J4T3 [CX3003]	ST72F325J4T5 [CX3003]
ST72F325J4T6 [CX3003]	ST72F325J6B3 [CX0042]
ST72F325J6B5 [CX0042]	ST72F325J6B6 [CX0042]
ST72F325J6T3 [CX3003]	ST72F325J6T5 [CX3003]
ST72F325J6T6 [CX3003]	ST72F325J7T3 [CX3003]
ST72F325J7T5 [CX3003]	ST72F325J7T6 [CX3003]
ST72F325J9T3 [CX3003]	ST72F325J9T5 [CX3003]
ST72F325J9T6 [CX3003]	ST72F325K4B3 [CX0032]
ST72F325K4B5 [CX0032]	ST72F325K4B6 [CX0032]
ST72F325K4T3 [CX3001]	ST72F325K4T5 [CX3001]
ST72F325K4T6 [CX3001]	ST72F325K6B3 [CX0032]
ST72F325K6B5 [CX0032]	ST72F325K6B6 [CX0032]
ST72F325K6T3 [CX3001]	ST72F325K6T5 [CX3001]
ST72F325K6T6 [CX3001]	ST72F325R6T3 [CX3013]
ST72F325R6T5 [CX3013]	ST72F325R6T6 [CX3013]
ST72F325R7T3 [CX3013]	ST72F325R7T5 [CX3013]
ST72F325R7T6 [CX3013]	ST72F325R9T3 [CX3013]
ST72F325R9T5 [CX3013]	ST72F325R9T6 [CX3013]
ST72F521AR6T3 [CX3011]	ST72F521AR6T6 [CX3011]
ST72F521AR6TC [CX3011]	ST72F521AR9T3 [CX3011]
ST72F521AR9T6 [CX3011]	ST72F521AR9TC [CX3011]
ST72F521BAR6T3 [CX3011]	ST72F521BAR6T6 [CX3011]
ST72F521BAR6TC [CX3011]	ST72F521BAR9T3 [CX3011]
ST72F521BAR9T6 [CX3011]	ST72F521BAR9TC [CX3011]
ST72F521BM9T3 [CX3054]	ST72F521BM9T6 [CX3054]
ST72F521BM9TC [CX3054]	ST72F521BR6T3 [CX3013]
ST72F521BR6T6 [CX3013]	ST72F521BR6TC [CX3013]
ST72F521BR9T3 [CX3013]	ST72F521BR9T6 [CX3013]
ST72F521BR9TC [CX3013]	ST72F521M9T3 [CX3054]
ST72F521M9T6 [CX3054]	ST72F521M9TC [CX3054]
ST72F521R6T3 [CX3013]	ST72F521R6T6 [CX3013]
ST72F521R6TC [CX3013]	ST72F521R9T3 [CX3013]
ST72F521R9T6 [CX3013]	ST72F521R9TC [CX3013]

## ALTERA

### E (E) PROM/FRAM/NVRAM

EPC1(LC)@PLCC20 [CX2020]	EPC1(LI)@PLCC20 [CX2020]
EPC1(PC8) [CX0001]	EPC1(PI8) [CX0001]
EPC1213-LC20 [CX2020]	EPC1213-LI20 [CX2020]
EPC1213-PC8 [CX0001]	EPC1213-PI8 [CX0001]
EPC1441(LC)@PLCC20 [CX2020]	EPC1441(LI)@PLCC20 [CX2020]
EPC1441(PC8) [CX0001]	EPC1441(PI8) [CX0001]
EPC1441(TC)@TQFP32 [CX3001]	EPC1441(TI)@TQFP32 [CX3001]
EPC16QC100@PQFP100 [CX3045]	EPC16QI100@PQFP100 [CX3045]



EPC16UC88@BGA88 [CX5001]  
EPC16UC88AB@BGA88 [CX5001]  
EPC16UI88AA@BGA88 [CX5001]  
EPC2(LI)@PLCC20 [CX2020]  
EPC2(TI)@TQFP32 [CX3001]  
EPC4QC100N@PQFP100 [CX3045]  
EPC8QC100@PQFP100 [CX3045]  
EPC8QI100@PQFP100 [CX3045]  
EPCS16@SOIC16 [CX1033#1]  
EPCS1SI8@SOIC8 [CX1016]  
EPCS64@SOIC16 [CX1033#1]  
EPC16UC88AA@BGA88 [CX5001]  
EPC16UC88N@BGA88 [CX5001]  
EPC2(LC)@PLCC20 [CX2020]  
EPC2(TC)@TQFP32 [CX3001]  
EPC4QC100@PQFP100 [CX3045]  
EPC4QI100@PQFP100 [CX3045]  
EPC8QC100DM@PQFP100 [CX3045]  
EPCS128@SOIC16 [CX1033#1]  
EPCS16@SOIC8 [CX1045#1]  
EPCS4SI8@SOIC8 [CX1016]

## PLD

5M160Z@EQFP64 [CX3085]  
5M160Z@MBGA68 [CX5191]  
5M240Z@MBGA100 [CX5142]  
5M240Z@TQFP100 [CX3021]  
5M80Z@EQFP64 [CX3085]  
5M80Z@TQFP100 [CX3021]  
EP1810@PLCC68 [CX2068]  
EP1830@PLCC68 [CX2068]  
EP310@PLCC20 [CX2020]  
EP320@PLCC20 [CX2020]  
EP330@PLCC20 [CX2020]  
EP600@PLCC28 [CX2028]  
EP600I [CX0001]  
EP600I@SOIC24 [CX1033]  
EP610@PLCC28 [CX2028]  
EP610A [CX0001]  
EP610A@SOIC24 [CX1033]  
EP610I@PLCC28 [CX2028]  
EP610T [CX0001]  
EP610T@SOIC24 [CX1033]  
EP630@PLCC28 [CX2028]  
EP900 [CX0001]  
EP900I [CX0001]  
EP910 [CX0001]  
EP910A [CX0001]  
EP910I [CX0001]  
EP910T [CX0001]  
EPM240@FBGA100 [CX5059]  
EPM240@TQFP100 [CX3021]  
EPM240G@MBGA100 [CX5142]  
EPM240Z@MBGA100 [CX5142]  
EPM3032A@PLCC44 [CX2044]  
EPM5128A@PLCC68 [CX2068]  
EPM5130A@PQFP100 [CX3022]  
EPM7032@TQFP44 [CX3003]  
EPM7032AE@JLCC44(7032 mode) [CX2044]  
EPM7032AE@PLCC44(7032 mode) [CX2044]  
EPM7032AE@PLCC44(7032AE mode) [CX2044]  
EPM7032AE@PLCC44(7032S mode) [CX2044]  
EPM7032AE@PQFP44(7032 mode) [CX3003]  
EPM7032AE@TQFP44(7032 mode) [CX3003]  
EPM7032AE@TQFP44(7032AE mode) [CX3003]  
EPM7032AE@TQFP44(7032S mode) [CX3003]  
EPM7032S@PLCC44(7032 mode) [CX2044]  
EPM7032S@PLCC44(7032S mode) [CX2044]  
5M160Z@MBGA100 [CX5142]  
5M160Z@TQFP100 [CX3021]  
5M240Z@MBGA68 [CX5191]  
5M40Z@EQFP64 [CX3085]  
5M80Z@MBGA68 [CX5191]  
EP1800@PLCC68 [CX2068]  
EP1810T@PLCC68 [CX2068]  
EP310 [CX0001]  
EP320 [CX0001]  
EP330 [CX0001]  
EP600 [CX0001]  
EP600@SOIC24 [CX1033]  
EP600I@PLCC28 [CX2028]  
EP610 [CX0001]  
EP610@SOIC24 [CX1033]  
EP610A@PLCC28 [CX2028]  
EP610I [CX0001]  
EP610I@SOIC24 [CX1033]  
EP610T@PLCC28 [CX2028]  
EP630 [CX0001]  
EP630@SOIC24 [CX1033]  
EP900@PLCC44 [CX2044]  
EP900I@PLC44 [CX2044]  
EP910@PLCC44 [CX2044]  
EP910A@PLCC44 [CX2044]  
EP910I@PLCC44 [CX2044]  
EP910T@PLCC44 [CX2044]  
EPM240@MBGA100 [CX5142]  
EPM240G@FBGA100 [CX5059]  
EPM240G@TQFP100 [CX3021]  
EPM240Z@MBGA68 [CX5191]  
EPM3032A@TQFP44 [CX3003]  
EPM5130A@PLCC84 [CX2084]  
EPM7032@PLCC44 [CX2044]

EPM7032S@TQFP44(7032 mode) [CX3003]  
EPM7032S@TQFP44(7032S mode) [CX3003]  
EPM7032V@PLCC44 [CX2044] EPM7032V@TQFP44 [CX3003]  
EPM7064@PLCC44 [CX2044] EPM7064@TQFP44 [CX3003]  
EPM7064AE@FBGA100(7064AE mode) [CX5059]  
EPM7064AE@FBGA100(7064S mode) [CX5059]  
EPM7064AE@PLCC44(7064AE mode) [CX2044]  
EPM7064AE@PLCC44(7064S mode) [CX2044]  
EPM7064AE@PLCC84(7064AE mode) [CX2084]  
EPM7064AE@PLCC84(7064S mode) [CX2084]  
EPM7064AE@TQFP100(7064AE mode) [CX3021]  
EPM7064AE@TQFP100(7064S mode) [CX3021]  
EPM7064AE@TQFP44(7064AE mode) [CX3003]  
EPM7064AE@TQFP44(7064S mode) [CX3003]  
EPM7064AE@UBGA49(7064AE mode) [CX5112]  
EPM7064AE@UBGA49(7064S mode) [CX5112]  
EPM7064S@PLCC44(7064 mode) [CX2044]  
EPM7064S@PLCC44(7064S mode) [CX2044]  
EPM7064S@PLCC68(7064 mode) [CX2068]  
EPM7064S@PLCC68(7064S mode) [CX2068]  
EPM7064S@PLCC84(7064 mode) [CX2084]  
EPM7064S@PLCC84(7064S mode) [CX2084]  
EPM7064S@TQFP44(7064 mode) [CX3003]  
EPM7064S@TQFP44(7064S mode) [CX3003]  
EPM7128ELC(I)84(7128 mode) [CX2084]  
EPM7128ELC84(7128E mode) [CX2084]  
EPM7128ELI84(7128E mode) [CX2084]  
EPM7128SLC(I)84(7128 mode) [CX2084]  
EPM7128SLC(I)84(7128E mode) [CX2084]  
EPM7128SLC84(7128S/A mode) [CX2084]  
EPM7128SLI84(7128S/A mode) [CX2084]  
EPM7160ELC(I)84(7160 mode) [CX2084]  
EPM7160ELC84(7160E mode) [CX2084]  
EPM7160ELI84(7160E mode) [CX2084]  
EPM7160EQC(I)160(7160 mode) [CX3104]  
EPM7256AE@FBGA100(7256A mode) [CX5059]  
EPM7256AE@FBGA100(7256AE mode) [CX5059]  
EPM7256AE@FBGA100(7256S mode) [CX5059]  
EPM7256AE@TQFP100(7256A mode) [CX3021]  
EPM7256AE@TQFP100(7256AE mode) [CX3021]  
EPM7256AE@TQFP100(7256S mode) [CX3021]

## AMD

### E (E) PROM/FRAM/NVRAM

AM25FL005D@SOIC8 [CX1045]	AM25FL005D@USON8 [CX4005]
AM25FL010D@SOIC8 [CX1045]	AM25FL010D@USON8 [CX4005]
AM25FL016A@SOIC16 [CX1033#1]	AM25FL016A@SOIC16(ISP) [CX0001]
AM25FL016A@WSON8 [CX4006#1]	AM25FL016A@WSON8(ISP) [CX0001]
AM25FL020D@SOIC8 [CX1045#1]	AM25FL020D@USON8 [CX4005#1]
AM25FL032A@SOIC16 [CX1033#1]	AM25FL032A@SOIC16(ISP) [CX0001]
AM25FL032A@WSON8 [CX4006#1]	AM25FL032A@WSON8(ISP) [CX0001]
AM25FL040D@SOIC8 [CX1045#1]	AM25FL040D@USON8 [CX4005#1]
AM25FL080D@SOIC8 [CX1045#1]	AM25FL080D@USON8 [CX4005#1]
AM27128 [CX0001]	AM27128(DC) [CX0001]
AM27128(DC)@PLCC32 [CX2032]	AM27128@PLCC32 [CX2032]
AM27128A [CX0001]	AM27128A(F) [CX0001]

AM27128A(F)@PLCC32 [CX2032]  
AM27128A(PC)@PLCC32 [CX2032]  
AM2716 [CX0001]  
AM27256 [CX0001]  
AM27256AP [CX0001]  
AM27256F [CX0001]  
AM27256PC [CX0001]  
AM2732 [CX0001]  
AM2732B [CX0001]  
AM27512@PLCC32 [CX2032]  
AM27512DC@PLCC32 [CX2032]  
AM27512F@PLCC32 [CX2032]  
AM27512PC@PLCC32 [CX2032]  
AM2764 [CX0001]  
AM2764A [CX0001]  
AM2764A(DC)@PLCC32 [CX2032]  
AM2764A(DI) [CX0001]  
AM2764A(F) [CX0001]  
AM2764A(JC) [CX0001]  
AM2764A(LCB) [CX0001]  
AM2764A(LEB) [CX0001]  
AM2764A(PC)@PLCC32 [CX2032]  
AM27C010 [CX0001]  
AM27C010@TSOP32 [CX1002]  
AM27C020@PLCC32 [CX2032]  
AM27C040 [CX0001]  
AM27C040@TSOP32 [CX1002]  
AM27C080@PLCC32 [CX2032]  
AM27C100 [CX0001]  
AM27C100@TSOP32 [CX1002]  
AM27C1024@PLCC44 [CX2044]  
AM27C128@PLCC32 [CX2032]  
AM27C2048@PLCC44 [CX2044]  
AM27C256 [CX0001]  
AM27C256(F)@PLCC32 [CX2032]  
AM27C256(PC)@PLCC32 [CX2032]  
AM27C400 [CX0001]  
AM27C4096 [CX0001]  
AM27C512 [CX0001]  
AM27C512(P)@PLCC32 [CX2032]  
AM27C64 [CX0001]  
AM27H010 [CX0001]  
AM27H010@TSOP32 [CX1002]  
AM27H256@PLCC32 [CX2032]  
AM27HB010@PLCC32 [CX2032]  
AM27LV010 [CX0001]  
AM27LV010@TSOP32 [CX1034]  
AM27LV010B@PLCC32 [CX2032]  
AM27LV020 [CX0001]  
AM27LV020@TSOP32 [CX1002]  
AM27LV020B@PLCC32 [CX2032]  
AM2816A [CX0001]  
AM2817A@PLCC32 [CX2032]  
AM2864A [CX0001]  
AM2864A(E)@PLCC32 [CX2032]  
AM2864B [CX0001]  
AM2864B(E)@PLCC32 [CX2032]  
AM28F001 [CX0001]  
AM28F001@TSOP32 [CX1002]  
AM27128A(PC) [CX0001]  
AM27128A@PLCC32 [CX2032]  
AM2716B [CX0001]  
AM27256@PLCC32 [CX2032]  
AM27256AP@PLCC32 [CX2032]  
AM27256F@PLCC32 [CX2032]  
AM27256PC@PLCC32 [CX2032]  
AM2732A [CX0001]  
AM27512 [CX0001]  
AM27512DC [CX0001]  
AM27512F [CX0001]  
AM27512PC [CX0001]  
AM27513 [CX0001]  
AM2764@PLCC32 [CX2032]  
AM2764A(DC) [CX0001]  
AM2764A(DCB) [CX0001]  
AM2764A(DIB) [CX0001]  
AM2764A(F)@PLCC32 [CX2032]  
AM2764A(LC) [CX0001]  
AM2764A(LE) [CX0001]  
AM2764A(PC) [CX0001]  
AM2764A@PLCC32 [CX2032]  
AM27C010@PLCC32 [CX2032]  
AM27C020 [CX0001]  
AM27C020@TSOP32 [CX1002]  
AM27C040@PLCC32 [CX2032]  
AM27C080 [CX0001]  
AM27C080@TSOP32 [CX1002]  
AM27C100@PLCC32 [CX2032]  
AM27C1024 [CX0001]  
AM27C128 [CX0001]  
AM27C2048 [CX0001]  
AM27C2048@TSOP40 [CX1006]  
AM27C256(F) [CX0001]  
AM27C256(PC) [CX0001]  
AM27C256@PLCC32 [CX2032]  
AM27C400@PLCC44 [CX2044]  
AM27C4096@PLCC44 [CX2044]  
AM27C512(P) [CX0001]  
AM27C512@PLCC32 [CX2032]  
AM27C64@PLCC32 [CX2032]  
AM27H010@PLCC32 [CX2032]  
AM27H256 [CX0001]  
AM27HB010 [CX0001]  
AM27HB010@TSOP32 [CX1002]  
AM27LV010@PLCC32 [CX2032]  
AM27LV010B [CX0001]  
AM27LV010B@TSOP32 [CX1002]  
AM27LV020@PLCC32 [CX2032]  
AM27LV020B [CX0001]  
AM27LV020B@TSOP32 [CX1002]  
AM2817A [CX0001]  
AM2817A@SOIC28 [CX1033]  
AM2864A(E) [CX0001]  
AM2864A@PLCC32 [CX2032]  
AM2864B(E) [CX0001]  
AM2864B@PLCC32 [CX2032]  
AM28F001@PLCC32 [CX2032]  
AM28F010 [CX0001]

AM28F010(REVERSE)@TSOP32 [CX1002]  
AM28F010@PLCC32 [CX2032] AM28F010@TSOP32 [CX1002]  
AM28F010A [CX0001]  
AM28F010A(REVERSE)@TSOP32 [CX1002]  
AM28F010A@PLCC32 [CX2032] AM28F010A@TSOP32 [CX1002]  
AM28F020 [CX0001]  
AM28F020(REVERSE)@TSOP32 [CX1002]  
AM28F020@PLCC32 [CX2032] AM28F020@TSOP32 [CX1002]  
AM28F020A [CX0001]  
AM28F020A(REVERSE)@TSOP32 [CX1002]  
AM28F020A@PLCC32 [CX2032] AM28F020A@TSOP32 [CX1002]  
AM28F256 [CX0001]  
AM28F256(REVERSE)@TSOP32 [CX1002]  
AM28F256@PLCC32 [CX2032] AM28F256@TSOP32 [CX1002]  
AM28F256A [CX0001]  
AM28F256A(REVERSE)@TSOP32 [CX1002]  
AM28F256A@PLCC32 [CX2032] AM28F256A@TSOP32 [CX1002]  
AM28F512 [CX0001]  
AM28F512(REVERSE)@TSOP32 [CX1002]  
AM28F512@PLCC32 [CX2032] AM28F512@TSOP32 [CX1002]  
AM28F512A [CX0001]  
AM28F512A(REVERSE)@TSOP32 [CX1002]  
AM28F512A@PLCC32 [CX2032] AM28F512A@TSOP32 [CX1002]  
AM28F512AF [CX0001]  
AM28F512AF(REVERSE)@TSOP32 [CX1002]  
AM28F512AF@PLCC32 [CX2032] AM28F512AF@TSOP32 [CX1002]  
AM28F512F [CX0001]  
AM28F512F(REVERSE)@TSOP32 [CX1002]  
AM28F512F@PLCC32 [CX2032] AM28F512F@TSOP32 [CX1002]  
AM29BDD160GB@FBGA80 [CX50UN] AM29BDD160GB@PQFP80 [CX3020]  
AM29BDD160GT@FBGA80 [CX50UN] AM29BDD160GT@PQFP80 [CX3020]  
AM29BL162CB@SSOP56 [CX1029] AM29BL802CB@SSOP56 [CX1029]  
AM29DL161DB@FBGA48 [CX5022] AM29DL161DB@FBGA63 [CX5047]  
AM29DL161DB@FBGA64 [CX5074] AM29DL161DB@TSOP48 [CX1004]  
AM29DL161DB@VFBGA48 [CX5043] AM29DL161DT@FBGA48 [CX5022]  
AM29DL161DT@FBGA63 [CX5047] AM29DL161DT@FBGA64 [CX5074]  
AM29DL161DT@TSOP48 [CX1004] AM29DL161DT@VFBGA48 [CX5043]  
AM29DL162CB@FBGA48 [CX5022] AM29DL162CB@TSOP48 [CX1004]  
AM29DL162CT@FBGA48 [CX5022] AM29DL162CT@TSOP48 [CX1004]  
AM29DL162DB@FBGA48 [CX5022] AM29DL162DB@FBGA63 [CX5047]  
AM29DL162DB@FBGA64 [CX5074] AM29DL162DB@TSOP48 [CX1004]  
AM29DL162DB@VFBGA48 [CX5043] AM29DL162DT@FBGA48 [CX5022]  
AM29DL162DT@FBGA63 [CX5047] AM29DL162DT@FBGA64 [CX5074]  
AM29DL162DT@TSOP48 [CX1004] AM29DL162DT@VFBGA48 [CX5043]  
AM29DL163CB@FBGA48 [CX5022] AM29DL163CB@TSOP48 [CX1004]  
AM29DL163CT@FBGA48 [CX5022] AM29DL163CT@TSOP48 [CX1004]  
AM29DL163DB@FBGA48 [CX5022] AM29DL163DB@FBGA63 [CX5047]  
AM29DL163DB@FBGA64 [CX5074] AM29DL163DB@TSOP48 [CX1004]  
AM29DL163DB@VFBGA48 [CX5043] AM29DL163DT@FBGA48 [CX5022]  
AM29DL163DT@FBGA63 [CX5047] AM29DL163DT@FBGA64 [CX5074]  
AM29DL163DT@TSOP48 [CX1004] AM29DL163DT@VFBGA48 [CX5043]  
AM29DL164CB@FBGA48 [CX5022] AM29DL164CB@TSOP48 [CX1004]  
AM29DL164CT@FBGA48 [CX5022] AM29DL164CT@TSOP48 [CX1004]  
AM29DL164DB@FBGA48 [CX5022] AM29DL164DB@FBGA63 [CX5047]  
AM29DL164DB@FBGA64 [CX5074] AM29DL164DB@TSOP48 [CX1004]  
AM29DL164DB@VFBGA48 [CX5043] AM29DL164DT@FBGA48 [CX5022]  
AM29DL164DT@FBGA63 [CX5047] AM29DL164DT@FBGA64 [CX5074]  
AM29DL164DT@TSOP48 [CX1004] AM29DL164DT@VFBGA48 [CX5043]  
AM29DL320GB@FBGA48 [CX5063] AM29DL320GB@FBGA63 [CX5051]

AM29DL320GB@FBGA64 [CX5074]	AM29DL320GB@TSOP48 [CX1004]
AM29DL320GT@FBGA48 [CX5063]	AM29DL320GT@FBGA63 [CX5051]
AM29DL320GT@FBGA64 [CX5074]	AM29DL320GT@TSOP48 [CX1004]
AM29DL321CB@TSOP48 [CX1004]	AM29DL321CT@TSOP48 [CX1004]
AM29DL322CB@FBGA63 [CX5051]	AM29DL322CB@TSOP48 [CX1004]
AM29DL322CT@FBGA63 [CX5051]	AM29DL322CT@TSOP48 [CX1004]
AM29DL322DB@FBGA63 [CX5051]	AM29DL322DB@TSOP48 [CX1004]
AM29DL322DT@FBGA63 [CX5051]	AM29DL322DT@TSOP48 [CX1004]
AM29DL322GB@FBGA48 [CX5063]	AM29DL322GB@FBGA63 [CX5051]
AM29DL322GB@FBGA64 [CX5074]	AM29DL322GB@TSOP48 [CX1004]
AM29DL322GT@FBGA48 [CX5063]	AM29DL322GT@FBGA63 [CX5051]
AM29DL322GT@FBGA64 [CX5074]	AM29DL322GT@TSOP48 [CX1004]
AM29DL323CB@FBGA63 [CX5051]	AM29DL323CB@TSOP48 [CX1004]
AM29DL323CT@FBGA63 [CX5051]	AM29DL323CT@TSOP48 [CX1004]
AM29DL323DB@FBGA48 [CX5022]	AM29DL323DB@FBGA63 [CX5051]
AM29DL323DB@TSOP48 [CX1004]	AM29DL323DT@FBGA48 [CX5022]
AM29DL323DT@FBGA63 [CX5051]	AM29DL323DT@TSOP48 [CX1004]
AM29DL323GB@FBGA48 [CX5063]	AM29DL323GB@FBGA63 [CX5051]
AM29DL323GB@FBGA64 [CX5074]	AM29DL323GB@TSOP48 [CX1004]
AM29DL323GT@FBGA48 [CX5063]	AM29DL323GT@FBGA63 [CX5051]
AM29DL323GT@FBGA64 [CX5074]	AM29DL323GT@TSOP48 [CX1004]
AM29DL324CB@TSOP48 [CX1004]	AM29DL324CT@TSOP48 [CX1004]
AM29DL324DB@FBGA63 [CX5051]	AM29DL324DB@TSOP48 [CX1004]
AM29DL324DT@FBGA63 [CX5051]	AM29DL324DT@TSOP48 [CX1004]
AM29DL324GB@FBGA48 [CX5063]	AM29DL324GB@FBGA63 [CX5051]
AM29DL324GB@FBGA64 [CX5074]	AM29DL324GB@TSOP48 [CX1004]
AM29DL324GT@FBGA48 [CX5063]	AM29DL324GT@FBGA63 [CX5051]
AM29DL324GT@FBGA64 [CX5074]	AM29DL324GT@TSOP48 [CX1004]
AM29DL400BB (REVERSE)@TSOP48 [CX1004]	
AM29DL400BB@PSOP44 [CX1014]	AM29DL400BB@TSOP48 [CX1004]
AM29DL400BT (REVERSE)@TSOP48 [CX1004]	
AM29DL400BT@PLCC44 [CX1014]	AM29DL400BT@TSOP48 [CX1004]
AM29DL640D@FBGA63 [CX5041]	AM29DL640D@TSOP48 [CX1004]
AM29DL640G@FBGA63 [CX5041]	AM29DL640G@FBGA64 [CX5074]
AM29DL640G@TSOP48 [CX1004]	AM29DL642G@FBGA63 [CX5041]
AM29DL800B@PSOP44 [CX1014]	AM29DL800B@TSOP48 [CX1004]
AM29DL800BB (REVERSE)@TSOP48 [CX1004]	
AM29DL800BB@FBGA48 [CX5039]	AM29DL800BB@PSOP44 [CX1014]
AM29DL800BB@TSOP48 [CX1004]	
AM29DL800BT (REVERSE)@TSOP48 [CX1004]	
AM29DL800BT@FBGA48 [CX5039]	AM29DL800BT@PSOP44 [CX1014]
AM29DL800BT@TSOP48 [CX1004]	AM29DL800T@PSOP44 [CX1014]
AM29DL800T@TSOP48 [CX1004]	AM29DS163CB@TSOP48 [CX1004]
AM29DS163CT@TSOP48 [CX1004]	AM29DS163DB@FBGA48 [CX5002]
AM29DS163DB@TSOP48 [CX1004]	AM29DS163DT@FBGA48 [CX5002]
AM29DS163DT@TSOP48 [CX1004]	AM29DS323DB@FBGA48 [CX5002]
AM29DS323DB@TSOP48 [CX1004]	AM29DS323DT@FBGA48 [CX5002]
AM29DS323DT@TSOP48 [CX1004]	AM29F002B [CX0001]
AM29F002B@PLCC32 [CX2032]	AM29F002B@TSOP32 [CX1002]
AM29F002BB [CX0001]	AM29F002BB@PLCC32 [CX2032]
AM29F002BB@TSOP32 [CX1002]	AM29F002BT [CX0001]
AM29F002BT@PLCC32 [CX2032]	AM29F002BT@TSOP32 [CX1002]
AM29F002NB [CX0001]	AM29F002NB@PLCC32 [CX2032]
AM29F002NB@TSOP32 [CX1002]	AM29F002NBB [CX0001]
AM29F002NBB@PLCC32 [CX2032]	AM29F002NBB@TSOP32 [CX1002]
AM29F002NBT [CX0001]	AM29F002NBT@PLCC32 [CX2032]
AM29F002NBT@TSOP32 [CX1002]	AM29F002NT [CX0001]
AM29F002NT@PLCC32 [CX2032]	AM29F002NT@TSOP32 [CX1002]
AM29F002T [CX0001]	AM29F002T@PLCC32 [CX2032]



AM29F002T@TSOP32 [CX1002] AM29F004BB [CX0001]  
AM29F004BB@PLCC32 [CX2032] AM29F004BB@TSOP32 [CX1002]  
AM29F004BT [CX0001] AM29F004BT@PLCC32 [CX2032]  
AM29F004BT@TSOP32 [CX1002] AM29F010 [CX0001]  
AM29F010(REVERSE)@TSOP32 [CX1002] AM29F010@TSOP32 [CX1002]  
AM29F010@PLCC32 [CX2032] AM29F010A@TSOP32 [CX1002]  
AM29F010A [CX0001] AM29F010A@TSOP32 [CX1002]  
AM29F010A(REVERSE)@TSOP32 [CX1002] AM29F010B@TSOP32 [CX1002]  
AM29F010A@PLCC32 [CX2032] AM29F016@TSOP40 [CX1006]  
AM29F010B [CX0001] AM29F016B@PSOP44 [CX1014]  
AM29F010B(REVERSE)@TSOP32 [CX1002] AM29F016B@TSOP48 [CX1004]  
AM29F010B@PLCC32 [CX2032] AM29F016B@TSOP40 [CX1006]  
AM29F016@PSOP44 [CX1014] AM29F016D@TSOP40 [CX1006]  
AM29F016@TSOP48 [CX1004] AM29F016D(REVERSE)@TSOP48 [CX1004]  
AM29F016B@TSOP40 [CX1006] AM29F016D@PSOP44 [CX1014]  
AM29F016D@TSOP48 [CX1004] AM29F016D@TSOP40 [CX1006]  
AM29F017B(REVERSE)@TSOP40 [CX1006] AM29F017B@TSOP48 [CX1004]  
AM29F017B(REVERSE)@TSOP48 [CX1004] AM29F017D@TSOP48 [CX1004]  
AM29F017B@TSOP40 [CX1006] AM29F032B@TSOP40 [CX1006]  
AM29F017D(REVERSE)@TSOP48 [CX1004] AM29F032B@PSOP44 [CX1014]  
AM29F017D@TSOP40 [CX1006] AM29F040 [CX0001]  
AM29F032B@PSOP44 [CX1014] AM29F040@PLCC32 [CX2032]  
AM29F040 [CX0001] AM29F040A [CX0001]  
AM29F040@TSOP32 [CX1002] AM29F040A@TSOP32 [CX1002]  
AM29F040A@PLCC32 [CX2032] AM29F040B [CX0001]  
AM29F040B [CX0001] AM29F040B(Reverse)@TSOP32 [CX1002]  
AM29F040B@TSOP32 [CX1002] AM29F040B@PLCC32 [CX2032]  
AM29F040B@TSOP32 [CX1002] AM29F080(REVERSE)@TSOP40 [CX1006]  
AM29F080@PSOP44 [CX1014] AM29F080@TSOP40 [CX1006]  
AM29F080B@PSOP44 [CX1014] AM29F080B@TSOP40 [CX1006]  
AM29F100B(REVERSE)@TSOP48 [CX1004] AM29F100B@TSOP48 [CX1004]  
AM29F100B@PSOP44 [CX1014] AM29F100T@TSOP48 [CX1004]  
AM29F100T(REVERSE)@TSOP48 [CX1004] AM29F100T@PSOP44 [CX1014]  
AM29F100T@PSOP44 [CX1014] AM29F160DB@TSOP48 [CX1004]  
AM29F160DB(REVERSE)@TSOP48 [CX1004] AM29F160DB@TSOP48(SLOW) [CX1043]  
AM29F160DB@TSOP48 [CX1004] AM29F160DT@TSOP48 [CX1004]  
AM29F160DT(REVERSE)@TSOP48 [CX1004] AM29F200AB@TSOP48 [CX1004]  
AM29F160DT@TSOP48 [CX1004] AM29F200AB@PSOP44 [CX1014]  
AM29F200AB(REVERSE)@TSOP48 [CX1004] AM29F200AT@TSOP48 [CX1004]  
AM29F200AB@PSOP44 [CX1014] AM29F200AT@PSOP44 [CX1014]  
AM29F200AT(REVERSE)@TSOP48 [CX1004] AM29F200AT@TSOP48 [CX1004]  
AM29F200AT@PSOP44 [CX1014] AM29F200BB@TSOP48 [CX1004]  
AM29F200BB(REVERSE)@TSOP48 [CX1004] AM29F200BB@PSOP44 [CX1014]  
AM29F200BB@PSOP44 [CX1014] AM29F200BB@TSOP48 [CX1004]  
AM29F200BT(REVERSE)@TSOP48 [CX1004] AM29F200BT@TSOP48 [CX1004]  
AM29F200BT@PSOP44 [CX1014] AM29F200BT@TSOP48 [CX1004]  
AM29F400AB(REVERSE)@TSOP48 [CX1004] AM29F400AB@TSOP48 [CX1004]  
AM29F400AB@PSOP44 [CX1014] AM29F400AT@TSOP48 [CX1004]  
AM29F400AT(REVERSE)@TSOP48 [CX1004] AM29F400AT@PSOP44 [CX1014]  
AM29F400AT@PSOP44 [CX1014] AM29F400BB@TSOP48 [CX1004]  
AM29F400BB(REVERSE)@TSOP48 [CX1004] AM29F400BB@PSOP44 [CX1014]  
AM29F400BB@PSOP44 [CX1014] AM29F400BB@TSOP48 [CX1004]  
AM29F400BT(REVERSE)@TSOP48 [CX1004] AM29F400BT@TSOP48 [CX1004]  
AM29F400BT@PSOP44 [CX1014] AM29F400BT@TSOP48 [CX1004]  
AM29F800B(REVERSE)@TSOP48 [CX1004] AM29F800B@TSOP48 [CX1004]  
AM29F800B@PSOP44 [CX1014] AM29F800B@TSOP48 [CX1004]

AM29F800BB(REVERSE)@TSOP48 [CX1004]  
AM29F800BB@FBGA48 [CX5039] AM29F800BB@PSOP44 [CX1014]  
AM29F800BB@TSOP48 [CX1004]  
AM29F800BT(REVERSE)@TSOP48 [CX1004]  
AM29F800BT@FBGA48 [CX5039] AM29F800BT@PSOP44 [CX1014]  
AM29F800BT@TSOP48 [CX1004]  
AM29F800T(REVERSE)@TSOP48 [CX1004]  
AM29F800T@PSOP44 [CX1014] AM29F800T@TSOP48 [CX1004]  
AM29LL800B@TSOP48 [CX1004] AM29LL800BB@TSOP48 [CX1004]  
AM29LL800BT@TSOP48 [CX1004] AM29LL800T@TSOP48 [CX1004]  
AM29LV001BB(REVERSE)@TSOP32 [CX1002]  
AM29LV001BB@PLCC32 [CX2032] AM29LV001BB@TSOP32 [CX1002]  
AM29LV001BT(REVERSE)@TSOP32 [CX1002]  
AM29LV001BT@PLCC32 [CX2032] AM29LV001BT@TSOP32 [CX1002]  
AM29LV002@TSOP40 [CX1006] AM29LV002B@TSOP40 [CX1006]  
AM29LV002BB@TSOP40 [CX1006] AM29LV002BT@TSOP40 [CX1006]  
AM29LV004B@TSOP40 [CX1006] AM29LV004BB@TSOP40 [CX1006]  
AM29LV004BT@TSOP40 [CX1006] AM29LV004T@TSOP40 [CX1006]  
AM29LV008B@TSOP40 [CX1006] AM29LV008BB@TSOP40 [CX1006]  
AM29LV008BT@TSOP40 [CX1006] AM29LV008T@TSOP40 [CX1006]  
AM29LV010B@PLCC32 [CX2032] AM29LV010B@TSOP32 [CX1002]  
AM29LV017B(REVERSE)@TSOP40 [CX1006]  
AM29LV017B@FBGA48 [CX5022] AM29LV017B@TSOP40 [CX1006]  
AM29LV017D(REVERSE)@TSOP40 [CX1006]  
AM29LV017D@FBGA48 [CX5022] AM29LV017D@TSOP40 [CX1006]  
AM29LV020B@PLCC32 [CX2032] AM29LV020B@TSOP32 [CX1002]  
AM29LV033C@FBGA63 [CX5051] AM29LV033C@TSOP40 [CX1006]  
AM29LV033MU@FBGA48 [CX5022] AM29LV033MU@TSOP40 [CX1006]  
AM29LV040B@PLCC32 [CX2032] AM29LV040B@TSOP32 [CX1002]  
AM29LV040E@PLCC32 [CX2032] AM29LV040E@TSOP32 [CX1002]  
AM29LV040J@PLCC32 [CX2032] AM29LV040J@TSOP32 [CX1002]  
AM29LV065D@FBGA63 [CX5041] AM29LV065D@TSOP48 [CX1004]  
AM29LV065MU@FBGA63 [CX5041] AM29LV065MU@TSOP48 [CX1004]  
AM29LV080@TSOP40 [CX1006] AM29LV081@TSOP40 [CX1006]  
AM29LV081B@TSOP40 [CX1006] AM29LV116BB@TSOP40 [CX1006]  
AM29LV116BT@TSOP40 [CX1006] AM29LV116DB@TSOP40 [CX1006]  
AM29LV116DT@TSOP40 [CX1006]  
AM29LV128MH(REVERSE)@TSOP56 [CX1011]  
AM29LV128MH@FBGA64 [CX5074] AM29LV128MH@TSOP56 [CX1011]  
AM29LV128ML(REVERSE)@TSOP56 [CX1011]  
AM29LV128ML@FBGA64 [CX5074] AM29LV128ML@TSOP56 [CX1011]  
AM29LV160BB(REVERSE)@TSOP48 [CX1004]  
AM29LV160BB@FBGA48 [CX5022] AM29LV160BB@PSOP44 [CX1014]  
AM29LV160BB@TSOP48 [CX1004]  
AM29LV160BT(REVERSE)@TSOP48 [CX1004]  
AM29LV160BT@FBGA48 [CX5022] AM29LV160BT@PSOP44 [CX1014]  
AM29LV160BT@TSOP48 [CX1004]  
AM29LV160DB(REVERSE)@TSOP48 [CX1004]  
AM29LV160DB@FBGA48 [CX5022] AM29LV160DB@PSOP44 [CX1014]  
AM29LV160DB@TSOP48 [CX1004]  
AM29LV160DB@TSOP48(SLOW) [CX1043]  
AM29LV160DT(REVERSE)@TSOP48 [CX1004]  
AM29LV160DT@FBGA48 [CX5022] AM29LV160DT@PSOP44 [CX1014]  
AM29LV160DT@TSOP48 [CX1004]  
AM29LV160DT@TSOP48(slow) [CX1043]  
AM29LV160MB(REVERSE)@TSOP48 [CX1004]  
AM29LV160MB@FBGA48 [CX5022] AM29LV160MB@FBGA64 [CX5074]  
AM29LV160MB@PSOP44 [CX1014] AM29LV160MB@TSOP48 [CX1004]  
AM29LV160MT(REVERSE)@TSOP48 [CX1004]

AM29LV160MT@FBGA48 [CX5022] AM29LV160MT@FBGA64 [CX5074]  
AM29LV160MT@PSOP44 [CX1014] AM29LV160MT@TSOP48 [CX1004]  
AM29LV200B(REVERSE)@TSOP48 [CX1004]  
AM29LV200B@PSOP44 [CX1014] AM29LV200B@TSOP48 [CX1004]  
AM29LV200BB(REVERSE)@TSOP48 [CX1004]  
AM29LV200BB@FBGA48 [CX5002] AM29LV200BB@PSOP44 [CX1014]  
AM29LV200BB@TSOP48 [CX1004]  
AM29LV200BT(REVERSE)@TSOP48 [CX1004]  
AM29LV200BT@FBGA48 [CX5002] AM29LV200BT@PSOP44 [CX1014]  
AM29LV200BT@TSOP48 [CX1004]  
AM29LV200T(REVERSE)@TSOP48 [CX1004]  
AM29LV200T@PSOP44 [CX1014] AM29LV200T@TSOP48 [CX1004]  
AM29LV256MH(REVERSE)@TSOP56 [CX1011]  
AM29LV256MH@FBGA64 [CX5075] AM29LV256MH@TSOP56 [CX1011]  
AM29LV256ML(REVERSE)@TSOP56 [CX1011]  
AM29LV256ML@FBGA64 [CX5075] AM29LV256ML@TSOP56 [CX1011]  
AM29LV320DB@FBGA48 [CX5040] AM29LV320DB@TSOP48 [CX1004]  
AM29LV320DT@FBGA48 [CX5040] AM29LV320DT@TSOP48 [CX1004]  
AM29LV320DT@TSOP48(slow) [CX1004]  
AM29LV320FB@TSOP48 [CX1004] AM29LV320FT@TSOP48 [CX1004]  
AM29LV320MB@FBGA48 [CX5022] AM29LV320MB@FBGA64 [CX5074]  
AM29LV320MB@TSOP48 [CX1004]  
AM29LV320MH(REVERSE)@TSOP56 [CX1011]  
AM29LV320MH@FBGA64 [CX5074] AM29LV320MH@TSOP56 [CX1011]  
AM29LV320ML(REVERSE)@TSOP56 [CX1011]  
AM29LV320ML@FBGA64 [CX5074] AM29LV320ML@TSOP56 [CX1011]  
AM29LV320MT@FBGA48 [CX5022] AM29LV320MT@FBGA64 [CX5074]  
AM29LV320MT@TSOP48 [CX1004]  
AM29LV400B(REVERSE)@TSOP48 [CX1004]  
AM29LV400B@FBGA48 [CX5002] AM29LV400B@PSOP44 [CX1014]  
AM29LV400B@TSOP48 [CX1004]  
AM29LV400BB(REVERSE)@TSOP48 [CX1004]  
AM29LV400BB@FBGA48 [CX5002] AM29LV400BB@PSOP44 [CX1014]  
AM29LV400BB@TSOP48 [CX1004]  
AM29LV400BT(REVERSE)@TSOP48 [CX1004]  
AM29LV400BT@FBGA48 [CX5002] AM29LV400BT@PSOP44 [CX1014]  
AM29LV400BT@TSOP48 [CX1004]  
AM29LV400T(REVERSE)@TSOP48 [CX1004]  
AM29LV400T@FBGA48 [CX5002] AM29LV400T@PSOP44 [CX1014]  
AM29LV400T@TSOP48 [CX1004] AM29LV640DH@SSOP56 [CX1029]  
AM29LV640DL@SSOP56 [CX1029] AM29LV640DU@FBGA63 [CX5041]  
AM29LV640DU@FBGA64 [CX5074] AM29LV640GU@FBGA63 [CX5041]  
AM29LV640GU@FBGA64 [CX5074] AM29LV640MB@FBGA63 [CX5041]  
AM29LV640MB@FBGA64 [CX5074] AM29LV640MB@TSOP48 [CX1004]  
AM29LV640MH(REVERSE)@TSOP56 [CX1011]  
AM29LV640MH@FBGA64 [CX5074] AM29LV640MH@TSOP56 [CX1011]  
AM29LV640ML(REVERSE)@TSOP56 [CX1011]  
AM29LV640ML@FBGA64 [CX5074] AM29LV640ML@TSOP56 [CX1011]  
AM29LV640MT@FBGA63 [CX5041] AM29LV640MT@FBGA64 [CX5074]  
AM29LV640MT@TSOP48 [CX1004] AM29LV640MU@FBGA63 [CX5041]  
AM29LV640MU@FBGA64 [CX5074]  
AM29LV641DH(REVERSE)@TSOP48 [CX1004]  
AM29LV641DH@TSOP48 [CX1004]  
AM29LV641DL(REVERSE)@TSOP48 [CX1004]  
AM29LV641DL@TSOP48 [CX1004]  
AM29LV641GH(REVERSE)@TSOP48 [CX1004]  
AM29LV641GH@TSOP48 [CX1004]  
AM29LV641GL(REVERSE)@TSOP48 [CX1004]  
AM29LV641GL@TSOP48 [CX1004]

AM29LV641MH(REVERSE)@TSOP48 [CX1004]  
AM29LV641MH@TSOP48 [CX1004]  
AM29LV641ML(REVERSE)@TSOP48 [CX1004]  
AM29LV641ML@TSOP48 [CX1004] AM29LV642D@FBGA64 [CX5074]  
AM29LV642G@FBGA64 [CX5074] AM29LV652D@FBGA63 [CX5041]  
AM29LV800B(REVERSE)@TSOP48 [CX1004]  
AM29LV800B@PSOP44 [CX1014] AM29LV800B@TSOP48 [CX1004]  
AM29LV800BB(REVERSE)@TSOP48 [CX1004]  
AM29LV800BB@FBGA48 [CX5039] AM29LV800BB@PSOP44 [CX1014]  
AM29LV800BB@TSOP48 [CX1004]  
AM29LV800BT(REVERSE)@TSOP48 [CX1004]  
AM29LV800BT@FBGA48 [CX5039] AM29LV800BT@PSOP44 [CX1014]  
AM29LV800BT@TSOP48 [CX1004]  
AM29LV800DB(REVERSE)@TSOP48 [CX1004]  
AM29LV800DB(WB)@FBGA48 [CX5039] AM29LV800DB(WC)@FBGA48 [CX5043]  
AM29LV800DB@PSOP44 [CX1014] AM29LV800DB@TSOP48 [CX1004]  
AM29LV800DT(REVERSE)@TSOP48 [CX1004]  
AM29LV800DT(WB)@FBGA48 [CX5039] AM29LV800DT(WC)@FBGA48 [CX5043]  
AM29LV800DT@PSOP44 [CX1014] AM29LV800DT@TSOP48 [CX1004]  
AM29LV800T(REVERSE)@TSOP48 [CX1004]  
AM29LV800T@PSOP44 [CX1014] AM29LV800T@TSOP48 [CX1004]  
AM29PDL128G70(REVERSE)@FBGA80 [CX5147]  
AM29PDL128G70@FBGA80 [CX5147] AM29PDL128G80@FBGA80 [CX5147]  
AM29PDL128G90@FBGA80 [CX5147] AM29PDS322DB@FBGA48 [CX50UN]  
AM29PDS322DT@FBGA48 [CX50UN] AM29PL160BB@PSOP44 [CX1014]  
AM29PL160BB@TSOP48 [CX1004] AM29PL160CB@PSOP44 [CX1014]  
AM29PL160CB@TSOP48 [CX1004] AM29PL160CT@PSOP44 [CX1014]  
AM29PL160CT@TSOP48 [CX1004] AM29SL160BB@FBGA48 [CX5022]  
AM29SL160BB@TSOP48 [CX1004] AM29SL160BT@FBGA48 [CX5022]  
AM29SL160BT@TSOP48 [CX1004] AM29SL160CB@FBGA48 [CX5022]  
AM29SL160CB@TSOP48 [CX1004] AM29SL160CT@FBGA48 [CX5022]  
AM29SL160CT@TSOP48 [CX1004] AM29SL400CB@FBGA48 [CX5002]  
AM29SL400CB@TSOP48 [CX1004] AM29SL400CT@FBGA48 [CX5002]  
AM29SL400CT@TSOP48 [CX1004]  
AM29SL800BB(REVERSE)@TSOP48 [CX1004]  
AM29SL800BB@FBGA48 [CX5039] AM29SL800BB@TSOP48 [CX1004]  
AM29SL800BT(REVERSE)@TSOP48 [CX1004]  
AM29SL800BT@FBGA48 [CX5039] AM29SL800BT@TSOP48 [CX1004]  
AM29SL800CB(REVERSE)@TSOP48 [CX1004]  
AM29SL800CB@FBGA48 [CX5039] AM29SL800CB@TSOP48 [CX1004]  
AM29SL800CT(REVERSE)@TSOP48 [CX1004]  
AM29SL800CT@FBGA48 [CX5039] AM29SL800CT@TSOP48 [CX1004]  
AM29SL800DB(REVERSE)@TSOP48 [CX1004]  
AM29SL800DB@TSOP48 [CX1004] AM29SL800DBUF@FBGA48 [CX5038]  
AM29SL800DEVG@FBGA48 [CX5038] AM29SL800DEVU@FBGA48 [CX5043]  
AM29SL800DBWA@FBGA48 [CX5002] AM29SL800DBWC@FBGA48 [CX5022]  
AM29SL800DT(REVERSE)@TSOP48 [CX1004]  
AM29SL800DT@TSOP48 [CX1004] AM29SL800DTUF@FBGA48 [CX5038]  
AM29SL800DTVG@FBGA48 [CX5038] AM29SL800DTVU@FBGA48 [CX5043]  
AM29SL800DTWA@FBGA48 [CX5002] AM29SL800DTWC@FBGA48 [CX5022]  
AM30LV0064DJ40@TSOP44 [CX1046] AM9716 [CX0001]  
AM9732 [CX0001] AM9732A [CX0001]  
AM9764 [CX0001] AM9764@PLCC32 [CX2032]  
AT29BDS640GB73@FBGA64 [CX50UN] AT29BDS640GB74@FBGA64 [CX50UN]  
AT29BDS640GB78@FBGA64 [CX50UN] AT29BDS640GB79@FBGA64 [CX50UN]  
AT29BDS640GB93@FBGA64 [CX50UN] AT29BDS640GB94@FBGA64 [CX50UN]  
AT29BDS640GB98@FBGA64 [CX50UN] AT29BDS640GB99@FBGA64 [CX50UN]  
AT29BDS640GT73@FBGA64 [CX50UN] AT29BDS640GT74@FBGA64 [CX50UN]  
AT29BDS640GT78@FBGA64 [CX50UN] AT29BDS640GT79@FBGA64 [CX50UN]

AT29BDS640GT93@FBGA64 [CX50UN]            AT29BDS640GT94@FBGA64 [CX50UN]  
AT29BDS640GT98@FBGA64 [CX50UN]            AT29BDS640GT99@FBGA64 [CX50UN]  
BS128HD5V(AM29BDS128HD)@FBGA80 [CX5053]  
BS128HD6V(AM29BDS128HD)@FBGA80 [CX5053]  
BS128HD8V(AM29BDS128HD)@FBGA80 [CX5053]  
BS128HD9V(AM29BDS128HD)@FBGA80 [CX5053]  
BS128HE5V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HE6V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HE8V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HE9V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HF5V(AM29BDS128HF)@FBGA80 [CX5053]  
BS128HF6V(AM29BDS128HF)@FBGA80 [CX5053]  
BS128HF8V(AM29BDS128HF)@FBGA80 [CX5053]  
BS128HF9V(AM29BDS128HF)@FBGA80 [CX5053]  
BS640HD8V(AM29BDS640HD)@FBGA64 [CX5053]  
BS640HD9V(AM29BDS640HD)@FBGA64 [CX5053]  
BS640HE8V(AM29BDS640HE)@FBGA64 [CX5053]  
BS640HE9V(AM29BDS640HE)@FBGA64 [CX5053]  
BS640HF8V(AM29BDS640HF)@FBGA64 [CX5053]  
BS640HF9V(AM29BDS640HF)@FBGA64 [CX5053]  
DS42514(AM29DL1634DB)@FBGA69 [CX5001]  
DS42515(AM29DL1644DB)@FBGA69 [CX5001]  
DS42516(AM29DL324DB)@FBGA73 [CX5001]  
DS42546(AM29DL1634DT)@FBGA69 [CX5001]  
DS42553(AM29DL323DT)@FBGA73 [CX5001]  
DS42585(AM29DL323DT)@FBGA73 [CX5001]  
DS42587(AM29DL324DB)@FBGA73 [CX5001]  
DS42629(AM29DL640G)@VFBGA48 [CX5080]  
DS42677(AM29LV128MH/L)@FBGA88 [CX5053]  
DS42678(AM29LV320MT)@FBGA67 [CX5001]  
DS42689(AM29LV320MT)@FBGA64 [CX5004]  
DS42690(AM29LV320MB)@FBGA64 [CX5004]  
DS42695(AM29LV320MT)@FBGA64 [CX5074]  
DS42696(AM29LV320MB)@FBGA64 [CX5074]  
DS42701(AM29LV640MU)@FBGA88 [CX5053]  
DS42725(AM50DL128CH)@FBGA88 [CX5001]  
DS42772A(AM29LV640M)@FBGA88 [CX5053]  
M410000000(AM41DL1614DT)@FBGA69 [CX5001]  
M410000001(AM41DL1614DB)@FBGA69 [CX5001]  
M410000002(AM41DL1614DT)@FBGA69 [CX5001]  
M410000003(AM41DL1614DB)@FBGA69 [CX5001]  
M410000004(AM41DL1624DT)@FBGA69 [CX5001]  
M410000005(AM41DL1624DB)@FBGA69 [CX5001]  
M410000006(AM41DL1624DT)@FBGA69 [CX5001]  
M410000007(AM41DL1624DB)@FBGA69 [CX5001]  
M410000008(AM41DL1634DT)@FBGA69 [CX5001]  
M410000009(AM41DL1634DB)@FBGA69 [CX5001]  
M41000000A(AM41DL1634DT)@FBGA69 [CX5001]  
M41000000B(AM41DL1634DB)@FBGA69 [CX5001]  
M41000000C(AM41DL1644DT)@FBGA69 [CX5001]  
M41000000D(AM41DL1644DB)@FBGA69 [CX5001]  
M41000000E(AM41DL1644DT)@FBGA69 [CX5001]  
M41000000F(AM41DL1644DB)@FBGA69 [CX5001]  
M41000000G(AM41DL6408G)@FBGA73 [CX5001]  
M41000000H(AM41DL6408G)@FBGA73 [CX5001]  
M41000001W(AM41DL3224GT)@FBGA73 [CX5001]  
M41000001X(AM41DL3224GB)@FBGA73 [CX5001]  
M41000001Y(AM41DL3224GT)@FBGA73 [CX5001]  
M41000001Z(AM41DL3224GB)@FBGA73 [CX5001]



M410000020 (AM41DL3234GT)@FBGA73 [CX5001]  
M410000021 (AM41DL3234GB)@FBGA73 [CX5001]  
M410000022 (AM41DL3234GT)@FBGA73 [CX5001]  
M410000023 (AM41DL3234GB)@FBGA73 [CX5001]  
M410000024 (AM41DL3244GT)@FBGA73 [CX5001]  
M410000025 (AM41DL3244GB)@FBGA73 [CX5001]  
M410000026 (AM41DL3244GT)@FBGA73 [CX5001]  
M410000027 (AM41DL3244GB)@FBGA73 [CX5001]  
M41000002L (AM41DL3228GT)@FBGA73 [CX5001]  
M41000002M (AM41DL3228GB)@FBGA73 [CX5001]  
M41000002N (AM41DL3228GT)@FBGA73 [CX5001]  
M41000002O (AM41DL3228GB)@FBGA73 [CX5001]  
M41000002P (AM41DL3238GT)@FBGA73 [CX5001]  
M41000002Q (AM41DL3238GB)@FBGA73 [CX5001]  
M41000002R (AM41DL3238GT)@FBGA73 [CX5001]  
M41000002S (AM41DL3238GB)@FBGA73 [CX5001]  
M41000002T (AM41DL3248GT)@FBGA73 [CX5001]  
M41000002U (AM41DL3248GB)@FBGA73 [CX5001]  
M41000002V (AM41DL3248GT)@FBGA73 [CX5001]  
M41000002W (AM41DL3248GB)@FBGA73 [CX5001]  
M41000003D (AM41DL3208GT)@FBGA73 [CX5001]  
M41000003E (AM41DL3208GB)@FBGA73 [CX5001]  
M41000003F (AM41DL3208GT)@FBGA73 [CX5001]  
M41000003G (AM41DL3208GB)@FBGA73 [CX5001]  
M410000095 (AM41LV3204MT)@FBGA69 [CX5005]  
M410000096 (AM41LV3204MB)@FBGA69 [CX5005]  
M41000009B (AM41DL6408H)@FBGA73 [CX5001]  
M41000009C (AM41DL6408H)@FBGA73 [CX5001]  
M41000009D (AM41DL6408H)@FBGA73 [CX5001]  
M420000000 (AM42DL640AG)@FBGA73 [CX5001]  
M420000001 (AM42DL640AG)@FBGA73 [CX5001]  
M420000004 (AM42DL1642DT)@FBGA69 [CX5001]  
M420000005 (AM42DL1642DB)@FBGA69 [CX5001]  
M420000006 (AM42DL1642DT)@FBGA69 [CX5001]  
M420000007 (AM42DL1642DB)@FBGA69 [CX5001]  
M42000000I (AM42DL1612DT)@FBGA69 [CX5001]  
M42000000J (AM42DL1612DB)@FBGA69 [CX5001]  
M42000000K (AM42DL1612DT)@FBGA69 [CX5001]  
M42000000L (AM42DL1612DB)@FBGA69 [CX5001]  
M42000000M (AM42DL1622DT)@FBGA69 [CX5001]  
M42000000N (AM42DL1622DB)@FBGA69 [CX5001]  
M42000000O (AM42DL1622DT)@FBGA69 [CX5001]  
M42000000P (AM42DL1622DB)@FBGA69 [CX5001]  
M42000000Q (AM42DL1632DT)@FBGA69 [CX5001]  
M42000000R (AM42DL1632DB)@FBGA69 [CX5001]  
M42000000S (AM42DL1632DT)@FBGA69 [CX5001]  
M42000000T (AM42DL1632DB)@FBGA69 [CX5001]  
M42000000U (AM42DL1642DT)@FBGA69 [CX5001]  
M42000000V (AM42DL1642DB)@FBGA69 [CX5001]  
M42000000W (AM42DL1642DT)@FBGA69 [CX5001]  
M42000000X (AM42DL1642DB)@FBGA69 [CX5001]  
M42000001A (AM42DL1614DT)@FBGA69 [CX5001]  
M42000001B (AM42DL1614DB)@FBGA69 [CX5001]  
M42000001C (AM42DL1614DT)@FBGA69 [CX5001]  
M42000001D (AM42DL1614DB)@FBGA69 [CX5001]  
M42000001E (AM42DL1624DT)@FBGA69 [CX5001]  
M42000001F (AM42DL1624DB)@FBGA69 [CX5001]  
M42000001G (AM42DL1624DT)@FBGA69 [CX5001]  
M42000001H (AM42DL1624DB)@FBGA69 [CX5001]

M42000001I (AM42DL1634DT)@FBGA69 [CX5001]  
M42000001J (AM42DL1634DB)@FBGA69 [CX5001]  
M42000001K (AM42DL1634DT)@FBGA69 [CX5001]  
M42000001L (AM42DL1634DB)@FBGA69 [CX5001]  
M42000001M (AM42DL1644DT)@FBGA69 [CX5001]  
M42000001N (AM42DL1644DB)@FBGA69 [CX5001]  
M42000001O (AM42DL1644DT)@FBGA69 [CX5001]  
M42000001P (AM42DL1644DB)@FBGA69 [CX5001]  
M420000022 (AM42DL3224GT)@FBGA73 [CX5001]  
M420000023 (AM42DL3224GB)@FBGA73 [CX5001]  
M420000024 (AM42DL3224GT)@FBGA73 [CX5001]  
M420000025 (AM42DL3224GB)@FBGA73 [CX5001]  
M420000026 (AM42DL3234GT)@FBGA73 [CX5001]  
M420000027 (AM42DL3234GB)@FBGA73 [CX5001]  
M420000028 (AM42DL3234GT)@FBGA73 [CX5001]  
M420000029 (AM42DL3234GB)@FBGA73 [CX5001]  
M42000002A (AM42DL3244GT)@FBGA73 [CX5001]  
M42000002B (AM42DL3244GB)@FBGA73 [CX5001]  
M42000002C (AM42DL3244GT)@FBGA73 [CX5001]  
M42000002D (AM42DL3244GB)@FBGA73 [CX5001]  
M42000002U (AM42DL6404G)@FBGA73 [CX5001]  
M42000002V (AM42DL6404G)@FBGA73 [CX5001]  
M42000002Y (AM42BDS6408GT)@FBGA93 [CX5001]  
M42000002Z (AM42BDS6408GB)@FBGA93 [CX5001]  
M420000030 (AM42BDS6408GT)@FBGA93 [CX5001]  
M420000031 (AM42BDS6408GB)@FBGA93 [CX5001]  
M420000032 (AM42BDS6408GT)@FBGA93 [CX5001]  
M420000033 (AM42BDS6408GB)@FBGA93 [CX5001]  
M420000034 (AM42BDS6408GT)@FBGA93 [CX5001]  
M420000035 (AM42BDS6408GB)@FBGA93 [CX5001]  
M42000004Y (AM42BDS640AGT)@FBGA93 [CX5001]  
M42000004Z (AM42BDS640AGB)@FBGA93 [CX5001]  
M420000050 (AM42BDS640AGT)@FBGA93 [CX5001]  
M420000051 (AM42BDS640AGB)@FBGA93 [CX5001]  
M420000052 (AM42BDS640AGT)@FBGA93 [CX5001]  
M420000053 (AM42BDS640AGB)@FBGA93 [CX5001]  
M420000054 (AM42BDS640AGT)@FBGA93 [CX5001]  
M420000055 (AM42BDS640AGB)@FBGA93 [CX5001]  
M42000005M (AM42DL6402G)@FBGA73 [CX5001]  
M42000005N (AM42DL6402G)@FBGA73 [CX5001]  
M42000005W (AM42DL3224GT)@FBGA73 [CX5001]  
M42000005X (AM42DL3224GB)@FBGA73 [CX5001]  
M42000005Y (AM42DL3234GT)@FBGA73 [CX5001]  
M42000005Z (AM42DL3234GB)@FBGA73 [CX5001]  
M420000060 (AM42DL3244GT)@FBGA73 [CX5001]  
M420000061 (AM42DL3244GB)@FBGA73 [CX5001]  
M420000070 (AM42BDS6408HE8)@BGA89 [CX5005]  
M420000071 (AM42BDS6408HE9)@BGA89 [CX5005]  
M420000072 (AM42BDS6408HD8)@BGA89 [CX5005]  
M420000073 (AM42BDS6408HD9)@BGA89 [CX5005]  
M420000074 (AM42BDS6408HE3)@BGA89 [CX5005]  
M420000075 (AM42BDS6408HE4)@BGA89 [CX5005]  
M420000076 (AM42BDS6408HD3)@BGA89 [CX5005]  
M420000077 (AM42BDS6408HD4)@BGA89 [CX5005]  
M420000078 (AM42DL640AH)@FBGA73 [CX5001]  
M420000079 (AM42DL640AH)@FBGA73 [CX5001]  
M450000000 (AM45DL6408G)@FBGA73 [CX5001]  
M450000001 (AM45DL6408G)@FBGA73 [CX5001]  
M450000008 (AM45DL3208GT)@FBGA73 [CX5001]

M450000009 (AM45DL3208GB)@FBGA73 [CX5001]  
M45000000A (AM45DL3208GT)@FBGA73 [CX5001]  
M45000000B (AM45DL3208GB)@FBGA73 [CX5001]  
M45000000S (AM45DL3228GT)@FBGA73 [CX5001]  
M45000000T (AM45DL3228GB)@FBGA73 [CX5001]  
M45000000U (AM45DL3228GT)@FBGA73 [CX5001]  
M45000000V (AM45DL3228GB)@FBGA73 [CX5001]  
M45000001C (AM45DL3238GT)@FBGA73 [CX5001]  
M45000001D (AM45DL3238GB)@FBGA73 [CX5001]  
M45000001E (AM45DL3238GT)@FBGA73 [CX5001]  
M45000001F (AM45DL3238GB)@FBGA73 [CX5001]  
M45000001W (AM45DL3248GT)@FBGA73 [CX5001]  
M45000001X (AM45DL3248GB)@FBGA73 [CX5001]  
M45000001Y (AM45DL3248GT)@FBGA73 [CX5001]  
M45000001Z (AM45DL3248GB)@FBGA73 [CX5001]  
M490000000 (AM49DL640BG)@FBGA73 [CX5001]  
M490000001 (AM49DL640BG)@FBGA73 [CX5001]  
M49000000G (AM49DL320BGT)@FBGA73 [CX5001]  
M49000000H (AM49DL320BGT)@FBGA73 [CX5001]  
M49000000J (AM49DL322BGT)@FBGA73 [CX5001]  
M49000000K (AM49DL322BGT)@FBGA73 [CX5001]  
M49000000L (AM49DL322BGB)@FBGA73 [CX5001]  
M49000000M (AM49DL322BGB)@FBGA73 [CX5001]  
M49000000N (AM49DL323BGT)@FBGA73 [CX5001]  
M49000000O (AM49DL323BGT)@FBGA73 [CX5001]  
M49000000P (AM49DL323BGB)@FBGA73 [CX5001]  
M49000000Q (AM49DL323BGB)@FBGA73 [CX5001]  
M49000000R (AM49DL324BGT)@FBGA73 [CX5001]  
M49000000S (AM49DL324BGT)@FBGA73 [CX5001]  
M49000000T (AM49DL324BGB)@FBGA73 [CX5001]  
M49000000U (AM49DL324BGB)@FBGA73 [CX5001]  
M49000001A (AM49DL320BGB)@FBGA73 [CX5001]  
M49000001B (AM49DL320BGB)@FBGA73 [CX5001]  
M49000001Y (AM49PDL640AG)@FBGA73 [CX5072]  
M49000001Z (AM49PDL640AG)@FBGA73 [CX5072]  
M490000025 (AM49DL640AG)@FBGA73 [CX5001]  
M490000026 (AM49DL640AG)@FBGA73 [CX5001]  
M490000028 (AM49PDL127BH)@FBGA73 [CX5001]  
M490000029 (AM49PDL127BH)@FBGA73 [CX5001]  
M49000002I (AM49PDL127AH)@FBGA73 [CX5001]  
M49000002J (AM49PDL127AH)@FBGA73 [CX5001]  
M49000002T (AM49LV6408MT)@FBGA69 [CX5005]  
M49000002U (AM49LV6408MB)@FBGA69 [CX5005]  
M49000002V (AM49LV6408MT)@FBGA69 [CX5005]  
M49000002X (AM49LV6408MB)@FBGA69 [CX5005]  
M490000030 (AM49PDL129BH)@FBGA73 [CX5001]  
M490000031 (AM49PDL129BH)@FBGA73 [CX5001]  
M490000032 (AM49DL3208GB)@FBGA69 [CX5001]  
M490000032 (AM49DL3208GT)@FBGA69 [CX5005]  
M490000034 (AM49DL3208GT)@FBGA69 [CX5005]  
M490000035 (AM49DL3208GB)@FBGA69 [CX5001]  
M49000003A (AM49DL640BH)@FBGA73 [CX5001]  
M49000003B (AM49DL640BH)@FBGA73 [CX5001]  
M49000003C (AM49DL640BH)@FBGA73 [CX5001]  
M49000003D (AM49DL640AH)@FBGA73 [CX5001]  
M49000003E (AM49DL640AH)@FBGA73 [CX5001]  
M49000003F (AM49DL6408H)@FBGA73 [CX5001]  
M49000003G (AM49DL6408H)@FBGA73 [CX5001]  
M49000003H (AM49DL6408H)@FBGA73 [CX5001]

M49000003I (AM49DL6408H)@FBGA73 [CX5001]  
M49000003J (AM49DL640AH)@FBGA73 [CX5001]  
M49000003X (AM49DL6408H)@FBGA73 [CX5001]  
M49000003Y (AM49DL6408H)@FBGA73 [CX5001]  
M49000003Z (AM49LV6408MT)@FBGA69 [CX5005]  
M49000004A (AM49LV6408MB)@FBGA69 [CX5005]  
M49000004B (AM49BDS640AH)@FBGA89 [CX5005]  
M49000004C (AM49BDS640AH)@FBGA89 [CX5005]  
M49000004D (AM49BDS640AH)@FBGA89 [CX5005]  
M49000004E (AM49BDS640AH)@FBGA89 [CX5005]  
M49000004H (AM49LV128BMH)@FBGA64 [CX5054]  
M49000004J (AM49LV128BML)@FBGA64 [CX5054]  
M49000004K (AM49LV128BMH)@FBGA64 [CX5054]  
M49000004L (AM49LV128BML)@FBGA64 [CX5054]  
M49000004S (AM49LV128BmaH)@FBGA64 [CX5054]  
M49000004T (AM49LV128BmaL)@FBGA64 [CX5054]  
M49000004U (AM49LV128BmaH)@FBGA64 [CX5054]  
M49000004V (AM49LV128BmaL)@FBGA64 [CX5054]  
M4900000K (AM49PDL129AH)@FBGA73 [CX5001]  
M4900000L (AM49PDL129AH)@FBGA73 [CX5001]  
M500000000 (AM50DL128BG)@FBGA73 [CX5001]  
M500000001 (AM50DL128BG)@FBGA73 [CX5001]  
M500000008 (AM50DL128CG)@FBGA88 [CX5001]  
M500000009 (AM50DL128CG)@FBGA88 [CX5001]  
M50000004J (AM50DL128BH)@FBGA73 [CX5001]  
M50000004K (AM50DL128BH)@FBGA73 [CX5001]  
M50000004L (AM50DL128BH)@FBGA73 [CX5001]  
M50000004M (AM50DL128CH)@FBGA88 [CX5001]  
M50000004N (AM50DL128CH)@FBGA88 [CX5001]  
M50000004P (AM50DL128CH)@FBGA88 [CX5001]  
M550000000 (AM55DL128C8G)@FBGA93 [CX5028]  
M550000001 (AM55DL128C8G)@FBGA93 [CX5028]  
PDL127H53V (AM29PDL127H53)@FBGA80 [CX5053]  
PDL127H63V (AM29PDL127H63)@FBGA80 [CX5053]  
PDL127H68V (AM29PDL127H68)@FBGA80 [CX5053]  
PDL127H88V (AM29PDL127H88)@FBGA80 [CX5053]  
PDL129H53V (AM29PDL129H53)@FBGA80 [CX5053]  
PDL129H63V (AM29PDL129H63)@FBGA80 [CX5053]  
PDL129H68V (AM29PDL129H68)@FBGA80 [CX5053]  
PDL129H88V (AM29PDL129H88)@FBGA80 [CX5053]

## BPROM

AM27LS19 [CX0001]	AM27LS19@PLCC20 [CX2020]
AM27LS19@SOIC16 [CX1033]	AM27PS191 [CX0001]
AM27PS191@PLCC28 [CX2028]	AM27PS191@PLCC32 [CX2032]
AM27PS191@SOIC24 [CX0133]	AM27PS191A [CX0001]
AM27PS191A@PLCC28 [CX2028]	AM27PS191A@PLCC32 [CX2032]
AM27PS191A@SOIC24 [CX0133]	AM27PS291 [CX0001]
AM27PS291@PLCC28 [CX2028]	AM27PS291@PLCC32 [CX2032]
AM27PS291@SOIC24 [CX0133]	AM27PS291A [CX0001]
AM27PS291A@PLCC28 [CX2028]	AM27PS291A@PLCC32 [CX2032]
AM27PS291A@SOIC24 [CX0133]	AM27PS41 [CX0001]
AM27PS41@PLCC28 [CX2028]	AM27PS41@SOIC20 [CX1033]
AM27S13 [CX0001]	AM27S13@PLCC20 [CX2020]
AM27S13@SOIC16 [CX1033]	AM27S13A [CX0001]
AM27S13A@PLCC20 [CX2020]	AM27S13A@SOIC16 [CX1033]
AM27S18 [CX0001]	AM27S18@PLCC20 [CX2020]
AM27S18@SOIC16 [CX1033]	AM27S180 [CX0001]

AM27S180@PLCC28 [CX2028]  
AM27S180@SOIC24 [CX0133]  
AM27S180A@PLCC28 [CX2028]  
AM27S180A@SOIC24 [CX0133]  
AM27S181@PLCC28 [CX2028]  
AM27S181@SOIC24 [CX0133]  
AM27S181A@PLCC28 [CX2028]  
AM27S181A@SOIC24 [CX0133]  
AM27S184@PLCC28 [CX2028]  
AM27S185 [CX0001]  
AM27S185@SOIC18 [CX1033]  
AM27S185A@PLCC28 [CX2028]  
AM27S18A [CX0001]  
AM27S18A@SOIC16 [CX1033]  
AM27S19@PLCC20 [CX2020]  
AM27S190 [CX0001]  
AM27S190@PLCC32 [CX2032]  
AM27S190A [CX0001]  
AM27S190A@PLCC32 [CX2032]  
AM27S191 [CX0001]  
AM27S191@PLCC32 [CX2032]  
AM27S191A [CX0001]  
AM27S191A@PLCC32 [CX2032]  
AM27S191SA [CX0001]  
AM27S191SA@PLCC32 [CX2032]  
AM27S19A [CX0001]  
AM27S19A@SOIC16 [CX1033]  
AM27S19SA@PLCC20 [CX2020]  
AM27S20 [CX0001]  
AM27S20@SOIC16 [CX1033]  
AM27S21@PLCC20 [CX2020]  
AM27S21A [CX0001]  
AM27S21A@SOIC16 [CX1033]  
AM27S23@PLCC20 [CX2020]  
AM27S23A [CX0001]  
AM27S23A@SOIC20 [CX1033]  
AM27S25@PLCC28 [CX2028]  
AM27S25@SOIC24 [CX1033]  
AM27S25A@PLCC28 [CX2028]  
AM27S25A@SOIC24 [CX1033]  
AM27S25SA@PLCC28 [CX2028]  
AM27S25SA@SOIC24 [CX1033]  
AM27S27@SOIC24 [CX1033]  
AM27S27A@SOIC24 [CX1033]  
AM27S280@PLCC28 [CX2028]  
AM27S280@SOIC24 [CX0133]  
AM27S281@PLCC28 [CX2028]  
AM27S281@SOIC24 [CX0133]  
AM27S281A@PLCC28 [CX2028]  
AM27S281A@SOIC24 [CX0133]  
AM27S29@PLCC20 [CX2020]  
AM27S291 [CX0001]  
AM27S291@PLCC32 [CX2032]  
AM27S291A [CX0001]  
AM27S291A@PLCC32 [CX2032]  
AM27S291SA [CX0001]  
AM27S291SA@PLCC32 [CX2032]  
AM27S29A [CX0001]  
AM27S29A@PLCC20 [CX2020]

AM27S180@PLCC32 [CX2032]  
AM27S180A [CX0001]  
AM27S180A@PLCC32 [CX2032]  
AM27S181 [CX0001]  
AM27S181@PLCC32 [CX2032]  
AM27S181A [CX0001]  
AM27S181A@PLCC32 [CX2032]  
AM27S184 [CX0001]  
AM27S184@SOIC18 [CX1033]  
AM27S185@PLCC28 [CX2028]  
AM27S185A [CX0001]  
AM27S185A@SOIC18 [CX1033]  
AM27S18A@PLCC20 [CX2020]  
AM27S19 [CX0001]  
AM27S19@SOIC16 [CX1033]  
AM27S190@PLCC28 [CX2028]  
AM27S190@SOIC24 [CX0133]  
AM27S190A@PLCC28 [CX2028]  
AM27S190A@SOIC24 [CX0133]  
AM27S191@PLCC28 [CX2028]  
AM27S191@SOIC24 [CX0133]  
AM27S191A@PLCC28 [CX2028]  
AM27S191A@SOIC24 [CX0133]  
AM27S191SA@PLCC28 [CX2028]  
AM27S191SA@SOIC24 [CX0133]  
AM27S19A@PLCC20 [CX2020]  
AM27S19SA [CX0001]  
AM27S19SA@SOIC16 [CX1033]  
AM27S20@PLCC20 [CX2020]  
AM27S21 [CX0001]  
AM27S21@SOIC16 [CX1033]  
AM27S21A@PLCC20 [CX2020]  
AM27S23 [CX0001]  
AM27S23@SOIC20 [CX1033]  
AM27S23A@PLCC20 [CX2020]  
AM27S25 [CX0001]  
AM27S25@PLCC32 [CX2032]  
AM27S25A [CX0001]  
AM27S25A@PLCC32 [CX2032]  
AM27S25SA [CX0001]  
AM27S25SA@PLCC32 [CX2032]  
AM27S27 [CX0001]  
AM27S27A [CX0001]  
AM27S280 [CX0001]  
AM27S280@PLCC32 [CX2032]  
AM27S281 [CX0001]  
AM27S281@PLCC32 [CX2032]  
AM27S281A [CX0001]  
AM27S281A@PLCC32 [CX2032]  
AM27S29 [CX0001]  
AM27S29@SOIC20 [CX1033]  
AM27S291@PLCC28 [CX2028]  
AM27S291@SOIC24 [CX0133]  
AM27S291A@PLCC28 [CX2028]  
AM27S291A@SOIC24 [CX0133]  
AM27S291SA@PLCC28 [CX2028]  
AM27S291SA@SOIC24 [CX0133]  
AM27S29A@LCC20  
AM27S29A@SOIC20 [CX1033]

AM27S29SA [CX0001]  
AM27S29SA@SOIC20 [CX1033]  
AM27S31@PLCC28 [CX2028]  
AM27S31@SOIC24 [CX0133]  
AM27S31A@PLCC28 [CX2028]  
AM27S31A@SOIC24 [CX0133]  
AM27S33@PLCC20 [CX2020]  
AM27S33A [CX0001]  
AM27S33A@SOIC18 [CX1033]  
AM27S35@PLCC28 [CX2028]  
AM27S35@SOIC24 [CX1033]  
AM27S35A@PLCC28 [CX2028]  
AM27S35A@SOIC24 [CX1033]  
AM27S37@PLCC28 [CX2028]  
AM27S37@SOIC24 [CX1033]  
AM27S37A@PLCC28 [CX2028]  
AM27S37A@SOIC24 [CX1033]  
AM27S41@PLCC28 [CX2028]  
AM27S41A [CX0001]  
AM27S41A@SOIC20 [CX1033]  
AM27S43@PLCC28 [CX2028]  
AM27S43@SOIC24 [CX0133]  
AM27S43A@PLCC28 [CX2028]  
AM27S43A@SOIC24 [CX0133]  
AM27S45@PLCC28 [CX2028]  
AM27S45@SOIC24 [CX1033]  
AM27S45A@PLCC28 [CX2028]  
AM27S45A@SOIC24 [CX1033]  
AM27S45SA@PLCC28 [CX2028]  
AM27S45SA@SOIC24 [CX1033]  
AM27S47@PLCC28 [CX2028]  
AM27S47@SOIC24 [CX1033]  
AM27S47A@PLCC28 [CX2028]  
AM27S47A@SOIC24 [CX1033]  
AM27S47SA@PLCC28 [CX2028]  
AM27S47SA@SOIC24 [CX1033]  
AM27S49@PLCC28 [CX2028]  
AM27S49@SOIC24 [CX0133]  
AM27S49A@PLCC28 [CX2028]  
AM27S49A@SOIC24 [CX0133]  
AM27S49SA@PLCC28 [CX2028]  
AM27S49SA@SOIC24 [CX0133]

AM27S29SA@PLCC20 [CX2020]  
AM27S31 [CX0001]  
AM27S31@PLCC32 [CX2032]  
AM27S31A [CX0001]  
AM27S31A@PLCC32 [CX2032]  
AM27S33 [CX0001]  
AM27S33@SOIC18 [CX1033]  
AM27S33A@PLCC20 [CX2020]  
AM27S35 [CX0001]  
AM27S35@PLCC32 [CX2032]  
AM27S35A [CX0001]  
AM27S35A@PLCC32 [CX2032]  
AM27S37 [CX0001]  
AM27S37@PLCC32 [CX2032]  
AM27S37A [CX0001]  
AM27S37A@PLCC32 [CX2032]  
AM27S41 [CX0001]  
AM27S41@SOIC20 [CX1033]  
AM27S41A@PLCC28 [CX2028]  
AM27S43 [CX0001]  
AM27S43@PLCC32 [CX2032]  
AM27S43A [CX0001]  
AM27S43A@PLCC32 [CX2032]  
AM27S45 [CX0001]  
AM27S45@PLCC32 [CX2032]  
AM27S45A [CX0001]  
AM27S45A@PLCC32 [CX2032]  
AM27S45SA [CX0001]  
AM27S45SA@PLCC32 [CX2032]  
AM27S47 [CX0001]  
AM27S47@PLCC32 [CX2032]  
AM27S47A [CX0001]  
AM27S47A@PLCC32 [CX2032]  
AM27S47SA [CX0001]  
AM27S47SA@PLCC32 [CX2032]  
AM27S49 [CX0001]  
AM27S49@PLCC32 [CX2032]  
AM27S49A [CX0001]  
AM27S49A@PLCC32 [CX2032]  
AM27S49SA [CX0001]  
AM27S49SA@PLCC32 [CX2032]

## PLD

AMPAL18P8 [CX0001]  
AMPAL22V10 [CX0001]  
AMPAL22V10A [CX0001]  
M4-128/64@PQFP100 [CX3022]  
M4-128N/64@PLCC84 [CX2084]  
M4LV-128/64@TQFP100 [CX3021]  
M4LV-64/32@PLCC44 [CX2044]  
M4LV-64/32@TQFP48 [CX3007]  
MACH111@PLCC44 [CX2044]  
MACH130@PLCC84 [CX2084]  
MACH131@PLCC84 [CX2084]  
MACH131SP@TQFP100 [CX3021]  
MACH210@TQFP44 [CX3003]  
MACH210A@TQFP44 [CX3003]

AMPAL18P8@PLCC20 [CX2020]  
AMPAL22V10@PLCC28 [CX2028]  
AMPAL22V10A@PLCC28 [CX2028]  
M4-128/64@TQFP100 [CX3021]  
M4LV-128/64@PQFP100 [CX3022]  
M4LV-128N/64@PLCC84 [CX2084]  
M4LV-64/32@TQFP44 [CX3003]  
MACH110@PLCC44 [CX2044]  
MACH111@TQFP44 [CX3003]  
MACH131/1@PLCC84 [CX2084]  
MACH131SP@PQFP100 [CX3022]  
MACH210@PLCC44 [CX2044]  
MACH210A@PLCC44 [CX2044]  
MACH210AQ@PLCC44 [CX2044]

MACH210AQ@TQFP44 [CX3003]  
MACH215@PLCC44 [CX2044]  
MACH221@PLCC68 [CX2068]  
MACH231SP@PQFP100 [CX3022]  
MACH435@PLCC84 [CX2084]  
MACH446@PQFP100 [CX3022]  
MACHLV210@PLCC44 [CX2044]  
MACHLV436@PLCC84 [CX2084]  
MACHLV446@TQFP100 [CX3021]  
PAL10H8-2 [CX0001]  
PAL10L8-2 [CX0001]  
PAL12H6-2 [CX0001]  
PAL12L6-2 [CX0001]  
PAL14H4-2 [CX0001]  
PAL14L4-2 [CX0001]  
PAL16C1-2 [CX0001]  
PAL16H2-2 [CX0001]  
PAL16L2-2 [CX0001]  
PAL16L8A [CX0001]  
PAL16L8A-2 [CX0001]  
PAL16L8B [CX0001]  
PAL16L8B-4 [CX0001]  
PAL16L8H-10 [CX0001]  
PAL16L8H-10@SOIC20 [CX0001]  
PAL16R4 [CX0001]  
PAL16R4A-2 [CX0001]  
PAL16R4B [CX0001]  
PAL16R4B-4 [CX0001]  
PAL16R4H-10 [CX0001]  
PAL16R4H-10@SOIC20 [CX0001]  
PAL16R6 [CX0001]  
PAL16R6A-2 [CX0001]  
PAL16R6B [CX0001]  
PAL16R6B-4 [CX0001]  
PAL16R6H-15 [CX0001]  
PAL16R8A [CX0001]  
PAL16R8A-4 [CX0001]  
PAL16R8B-2 [CX0001]  
PAL16R8D [CX0001]  
PAL16R8H-10@PLCC20 [CX0001]  
PAL16R8H-15 [CX0001]  
PAL20L8-10/2 [CX0001]  
PAL20L8-10/2@SOIC24 [CX1033]  
PAL20L8-5@PLCC28 [CX2028]  
PAL20L8-7 [CX0001]  
PAL20L8-7@SOIC24 [CX1033]  
PAL20R4-10/2@PLCC28 [CX2028]  
PAL20R4-5 [CX0001]  
PAL20R4-5@SOIC24 [CX1033]  
PAL20R4-7@PLCC28 [CX2028]  
PAL20R6-10/2 [CX0001]  
PAL20R6-10/2@SOIC24 [CX1033]  
PAL20R6-5@PLCC28 [CX2028]  
PAL20R6-7 [CX0001]  
PAL20R6-7@SOIC24 [CX1033]  
PAL20R8-10/2@PLCC28 [CX2028]  
PAL20R8-5 [CX0001]  
PAL20R8-5@SOIC24 [CX1033]  
PAL20R8-7@PLCC28 [CX2028]

MACH211@PLCC44 [CX2044]  
MACH220@PLCC68 [CX2068]  
MACH231SP@PLCC84 [CX2084]  
MACH231SP@TQFP100 [CX3021]  
MACH436@PLCC84 [CX2084]  
MACH446@TQFP100 [CX3021]  
MACHLV210@TQFP44 [CX3003]  
MACHLV446@PQFP100 [CX3022]  
PAL10H8 [CX0001]  
PAL10L8 [CX0001]  
PAL12H6 [CX0001]  
PAL12L6 [CX0001]  
PAL14H4 [CX0001]  
PAL14L4 [CX0001]  
PAL16C1 [CX0001]  
PAL16H2 [CX0001]  
PAL16L2 [CX0001]  
PAL16L8 [CX0001]  
PAL16L8A@PLCC20 [CX2020]  
PAL16L8A-4 [CX0001]  
PAL16L8B-2 [CX0001]  
PAL16L8D [CX0001]  
PAL16L8H-10@PLCC20 [CX0001]  
PAL16L8H-15 [CX0001]  
PAL16R4A [CX0001]  
PAL16R4A-4 [CX0001]  
PAL16R4B-2 [CX0001]  
PAL16R4D [CX0001]  
PAL16R4H-10@PLCC20 [CX0001]  
PAL16R4H-15 [CX0001]  
PAL16R6A [CX0001]  
PAL16R6A-4 [CX0001]  
PAL16R6B-2 [CX0001]  
PAL16R6D [CX0001]  
PAL16R8 [CX0001]  
PAL16R8A-2 [CX0001]  
PAL16R8B [CX0001]  
PAL16R8B-4 [CX0001]  
PAL16R8H-10 [CX0001]  
PAL16R8H-10@SOIC20 [CX0001]  
PAL16X4 [CX0001]  
PAL20L8-10/2@PLCC28 [CX2028]  
PAL20L8-5 [CX0001]  
PAL20L8-5@SOIC24 [CX1033]  
PAL20L8-7@PLCC28 [CX2028]  
PAL20R4-10/2 [CX0001]  
PAL20R4-10/2@SOIC24 [CX1033]  
PAL20R4-5@PLCC28 [CX2028]  
PAL20R4-7 [CX0001]  
PAL20R4-7@SOIC24 [CX1033]  
PAL20R6-10/2@PLCC28 [CX2028]  
PAL20R6-5 [CX0001]  
PAL20R6-5@SOIC24 [CX1033]  
PAL20R6-7@PLCC28 [CX2028]  
PAL20R8-10/2 [CX0001]  
PAL20R8-10/2@SOIC24 [CX1033]  
PAL20R8-5@PLCC28 [CX2028]  
PAL20R8-7 [CX0001]  
PAL20R8-7@SOIC24 [CX1033]

PAL22V10 [CX0001]  
PAL22V10A [CX0001]  
PAL29M16H [CX0001]  
PALC16L8Q@PLCC20 [CX2020]  
PALC16L8Z@PLCC20 [CX2020]  
PALC16R4Q@PLCC20 [CX2020]  
PALC16R4Z@PLCC20 [CX2020]  
PALC16R6Q@PLCC20 [CX2020]  
PALC16R6Z@PLCC20 [CX2020]  
PALC16R8Q@PLCC20 [CX2020]  
PALC16R8Z@PLCC20 [CX2020]  
PALCE16V8H@PLCC20 [CX2020]  
PALCE16V8Q [CX0001]  
PALCE16V8Q@SOIC20 [CX1033]  
PALCE16V8Z@PLCC20 [CX2020]  
PALCE20RA10 [CX0001]  
PALCE20RA10@SOIC24 [CX1033]  
PALCE20RA10H@PLCC28 [CX2028]  
PALCE20RA10Q [CX0001]  
PALCE20RA10Q@SOIC24 [CX1033]  
PALCE20V8H@PLCC28 [CX2028]  
PALCE20V8Q [CX0001]  
PALCE20V8Q@SOIC24 [CX1003]  
PALCE22V10H@PLCC28 [CX2028]  
PALCE22V10Q [CX0001]  
PALCE22V10Q@SOIC24 [CX1003]  
PALCE22V10Z@PLCC28 [CX2028]  
PALCE26V12H/4 [CX0001]  
PALCE26V12H/4@SOIC28 [CX1033]  
PALCE26V12H-15@PLCC28 [CX0001]  
PALCE26V12H-20 [CX0001]  
PALCE26V12H-20@SOIC28 [CX0001]  
PALCE26V12H-25@PLCC28 [CX0001]  
PALCE29M16H [CX0001]  
PALCE29M16H@SOIC24 [CX1033]  
PALCE29MA16H@PLCC28 [CX2028]  
PALCE610 [CX0001]  
PALCE610@SOIC24 [CX1003]  
PALCE610H@PLCC28 [CX2028]  
PALCE630H [CX0001]  
PALCE630H-P28 [CX2028]  
PALLV16V8@PLCC20 [CX2020]  
PALLV16V8Z [CX0001]  
PALLV16V8Z@SOIC20 [CX1033]

PAL22V10@PLCC28 [CX2028]  
PAL22V10A@PLCC28 [CX2028]  
PALC16L8Q [CX0001]  
PALC16L8Z [CX0001]  
PALC16R4Q [CX0001]  
PALC16R4Z [CX0001]  
PALC16R6Q [CX0001]  
PALC16R6Z [CX0001]  
PALC16R8Q [CX0001]  
PALC16R8Z [CX0001]  
PALCE16V8H [CX0001]  
PALCE16V8H@SOIC20 [CX1033]  
PALCE16V8Q@PLCC20 [CX2020]  
PALCE16V8Z [CX0001]  
PALCE16V8Z@SOIC20 [CX1033]  
PALCE20RA10@PLCC28 [CX2028]  
PALCE20RA10H [CX0001]  
PALCE20RA10H@SOIC24 [CX1033]  
PALCE20RA10Q@PLCC28 [CX2028]  
PALCE20V8H [CX0001]  
PALCE20V8H@SOIC24 [CX1003]  
PALCE20V8Q@PLCC28 [CX2028]  
PALCE22V10H [CX0001]  
PALCE22V10H@SOIC24 [CX1003]  
PALCE22V10Q@PLCC28 [CX2028]  
PALCE22V10Z [CX0001]  
PALCE22V10Z@SOIC24 [CX1003]  
PALCE26V12H/4@PLCC28 [CX2028]  
PALCE26V12H-15 [CX0001]  
PALCE26V12H-15@SOIC28 [CX0001]  
PALCE26V12H-20@PLCC28 [CX0001]  
PALCE26V12H-25 [CX0001]  
PALCE26V12H-25@SOIC28 [CX0001]  
PALCE29M16H@PLCC28 [CX2028]  
PALCE29MA16H [CX0001]  
PALCE29MA16H@SOIC24 [CX1033]  
PALCE610@PLCC28 [CX2028]  
PALCE610H [CX0001]  
PALCE610H@SOIC24 [CX1003]  
PALCE630H@SOIC24 [CX1003]  
PALLV16V8 [CX0001]  
PALLV16V8@SOIC20 [CX1033]  
PALLV16V8Z@PLCC20 [CX2020]

## MICROCONTROLLER

AM8751H [CX0001]  
AM87C51 [CX0001]  
AM87C51@TQFP44 [CX3002]  
AM87C521@PLCC44 [CX2044]  
AM87C541 [CX0001]  
AM87C541@TQFP44 [CX3002]

AM8753H [CX0001]  
AM87C51@PLCC44 [CX2044]  
AM87C521 [CX0001]  
AM87C521@TQFP44 [CX3002]  
AM87C541@PLCC44 [CX2044]

## AMIC

### E (E) PROM/FRAM/NVRAM



A25L010 [CX0001] A25L010@SOP8[150mil] [CX1045#1]  
A25L010@SOP8[209mil] [CX1044#1] A25L010A [CX0001]  
A25L010A@SOP8 [CX1045#1] A25L010A@TSSOP8 [CX1044#1]  
A25L010A@USON8 [CX4002#1] A25L010A@WSON8 [CX4005#1]  
A25L016 [CX0001] A25L016@SOP8 [CX1044#1]  
A25L016T [CX4006#1] A25L016T@SOP16 [CX1033#1]  
A25L016T@SOP8(150mil) [CX1045#1] A25L016T@SOP8(209mil) [CX1044#1]  
A25L016T@WSON8 [CX4005#1] A25L016U [CX4005#1]  
A25L016U@SOP16 [CX1033#1] A25L016U@SOP8(150mil) [CX1045#1]  
A25L016U@SOP8(209mil) [CX1044#1] A25L016U@WSON8 [CX4005#1]  
A25L020 [CX0001] A25L020@SOP8[150mil] [CX1045#1]  
A25L020@SOP8[209mil] [CX1044#1] A25L020B [CX0001]  
A25L020B@SOP8[150mil] [CX1045#1] A25L020B@SOP8[209mil] [CX1044#1]  
A25L020C [CX0001] A25L020C@SOP8 [CX1045#1]  
A25L020C@USON8 [CX4002#1] A25L020C@WSON8 [CX4005#1]  
A25L032 [CX0001] A25L032(NEW) [CX0001]  
A25L032(NEW)@SOP16 [CX1033#1] A25L032(NEW)@SOP8 [CX1044#1]  
A25L032(OTP) [CX0001] A25L032(OTP)@SOP16 [CX1033#1]  
A25L032(OTP)@SOP8 [CX1044#1] A25L032@SOP16 [CX1033#1]  
A25L032@SOP8 [CX1044#1] A25L032A [CX0001]  
A25L032A@SOP16 [CX1033#1] A25L032A@SOP8 [CX1044#1]  
A25L040 [CX0001] A25L040@QFN8 [CX4005#1]  
A25L040@SOP16 [CX1033#1] A25L040@SOP8 [CX1045#1]  
A25L040A [CX0001] A25L040A@SOP8 [CX1045#1]  
A25L040A@WSON8 [CX4005#1] A25L05P(Bottom) [CX0001]  
A25L05P(Bottom)@QFN8 [CX4005#1]  
A25L05P(Bottom)[150mil]@SOP8 [CX1045#1]  
A25L05P(Bottom)[209mil]@SOP8 [CX1044#1]  
A25L05P(Top) [CX0001] A25L05P(Top)@QFN8 [CX4005#1]  
A25L05P(Top)[150mil]@SOP8 [CX1045#1]  
A25L05P(Top)[209mil]@SOP8 [CX1044#1]  
A25L080 [CX0001] A25L080@QFN8 [CX4005#1]  
A25L080@SOP16 A25L080@SOP8 [CX1044#1]  
A25L080A [CX0001] A25L080A@QFN8 [CX4005#1]  
A25L080A@SOP16 A25L080A@SOP8 [CX1044#1]  
A25L080B [CX0001] A25L080B@SOP8 [CX1044#1]  
A25L080B@WSON8 [CX4005#1] A25L10P(Bottom) [CX0001]  
A25L10P(Bottom)@QFN8 [CX4005#1]  
A25L10P(Bottom)[150mil]@SOP8 [CX1045#1]  
A25L10P(Bottom)[209mil]@SOP8 [CX1044#1]  
A25L10P(Top) [CX0001] A25L10P(Top)@QFN8 [CX4005#1]  
A25L10P(Top)[150mil]@SOP8 [CX1045#1]  
A25L10P(Top)[209mil]@SOP8 [CX1044#1]  
A25L16P(Bottom Boot)@QFN8 [CX4005#1]  
A25L16P(Bottom Boot)@QFN8(ISP) [CX0001]  
A25L16P(Bottom Boot)@SOP16 [CX1033#1]  
A25L16P(Bottom Boot)@SOP16(ISP) [CX0001]  
A25L16P(Bottom Boot)@SOP8 [CX1044#1]  
A25L16P(Bottom Boot)@SOP8(ISP) [CX0001]  
A25L16P(Top Boot)@QFN8 [CX4006#1]  
A25L16P(Top Boot)@QFN8(ISP) [CX0001]  
A25L16P(Top Boot)@SOP16 [CX1033#1]  
A25L16P(Top Boot)@SOP16(ISP) [CX0001]  
A25L16P(Top Boot)@SOP8 [CX1044#1]  
A25L16P(Top Boot)@SOP8(ISP) [CX0001]  
A25L20P(Bottom) [CX0001] A25L20P(Bottom)@QFN8 [CX4005#1]  
A25L20P(Bottom)[150mil]@SOP8 [CX1045#1]  
A25L20P(Bottom)[209mil]@SOP8 [CX1044#1]  
A25L20P(Top) [CX0001] A25L20P(Top)@QFN8 [CX4005#1]

A25L20P(Top)[150mil]@SOP8 [CX1045#1]  
A25L20P(Top)[209mil]@SOP8 [CX1044#1]  
A25L40P(Bottom) [CX0001] A25L40P(Bottom)@QFN8 [CX4005#1]  
A25L40P(Bottom)@SOP16 A25L40P(Bottom)@SOP8 [CX1045#1]  
A25L40P(Top) [CX0001] A25L40P(Top)@QFN8 [CX4005#1]  
A25L40P(Top)@SOP16 A25L40P(Top)@SOP8 [CX1045#1]  
A25L42P(Bottom Boot) [CX0001]  
A25L42P(Bottom Boot)@QFN8 [CX4005#1]  
A25L42P(Bottom Boot)@SOP16 [CX1033#1]  
A25L42P(Bottom Boot)@SOP8 [CX1045#1]  
A25L42P(Top Boot) [CX0001]  
A25L42P(Top Boot)@QFN8 [CX4005#1]  
A25L42P(Top Boot)@SOP16 [CX1033#1]  
A25L42P(Top Boot)@SOP8 [CX1045#1]  
A25L512 [CX0001] A25L512[150mil]@SOP8 [CX1045#1]  
A25L512[209mil]@SOP8 [CX1044#1] A25L5120 [CX0001]  
A25L5120[150mil]@SOP8 [CX1045] A25L5120[209mil]@SOP8 [CX1044]  
A25L512A [CX0001] A25L512A@SOP8 [CX1045#1]  
A25L512A@TSSOP8 [CX1044#1] A25L512A@USON8 [CX4002#1]  
A25L512A@WSON8 [CX4005#1] A25L80P [CX0001]  
A25L80P@QFN8 [CX4005#1] A25L80P@SOP16  
A25L80P@SOP8 [CX1044#1] A25L82P(Bottom Boot) [CX0001]  
A25L82P(Bottom Boot)@QFN8 [CX4005#1]  
A25L82P(Bottom Boot)@SOP16 [CX1033#1]  
A25L82P(Bottom Boot)@SOP8 [CX1044#1]  
A25L82P(Top Boot) [CX0001]  
A25L82P(Top Boot)@QFN8 [CX4005#1]  
A25L82P(Top Boot)@SOP16 [CX1033#1]  
A25L82P(Top Boot)@SOP8 [CX1044#1]  
A25LQ032A [CX0001] A25LQ032A@SOP16 [CX1033#1]  
A25LQ032A@SOP8 [CX1044#1] A25LQ32B [CX0001]  
A25LQ32B@SOP8 [CX1044#1] A25LQ32B@WSON8 [CX4005#1]  
A25LQ64@BGA24 [CX5146] A25LQ64@SOP16 [CX1033#1]  
A25LQ64@SOP8 [CX1044#1] A25LQ64@WSON8 [CX4005#1]  
A25LS080 [CX0001] A25LS080@QFN8 [CX4005#1]  
A25LS080@SOP16 [CX1033#1] A25LS080@SOP8 [CX1044#1]  
A25LS512 [CX0001] A25LS512[150mil]@SOP8 [CX1045#1]  
A25LS512[209mil]@SOP8 [CX1044#1] A25LS5120 [CX0001]  
A25LS5120[150mil]@SOP8 [CX1045#1]  
A25LS5120[209mil]@SOP8 [CX1044#1]  
A27020 [CX0001] A27020@PLCC32 [CX2032]  
A27020@TSOP32 [CX1002] A27020L [CX0001]  
A27020L@PLCC32 [CX2032] A27020L@TSOP32 [CX1002]  
A275308 [CX0001] A275308@PLCC32 [CX2032]  
A276308 [CX0001] A276308(E) [CX0001]  
A276308(E)@PLCC32 [CX2032] A276308(E)@SOIC28 [CX1033]  
A276308@PLCC32 [CX2032] A276308@SOIC28 [CX1033]  
A276308A [CX0001] A276308A(L) [CX0001]  
A276308A(L)@PLCC32 [CX2032] A276308A(L)@SOIC28 [CX1033]  
A276308A@PLCC32 [CX2032] A276308A@SOIC28 [CX1033]  
A277308 [CX0001] A277308@PLCC32 [CX2032]  
A277308A [CX0001] A277308A@PLCC32 [CX2032]  
A278308 [CX0001] A278308@PLCC32 [CX2032]  
A278308A [CX0001] A278308A(L) [CX0001]  
A278308A(L)@PLCC32 [CX2032] A278308A@PLCC32 [CX2032]  
A279308 [CX0001] A279308@PLCC32 [CX2032]  
A290011T [CX0001] A290011T@PLCC32 [CX2032]  
A290011T@TSOP32 [CX1002] A290011U [CX0001]  
A290011U@PLCC32 [CX2032] A290011U@TSOP32 [CX1002]

A29001T [CX0001]  
A29001T@TSOP32 [CX1002]  
A29001U@PLCC32 [CX2032]  
A290021T [CX0001]  
A290021T@TSOP32 [CX1002]  
A290021U@PLCC32 [CX2032]  
A29002T [CX0001]  
A29002T@TSOP32 [CX1002]  
A29002U@PLCC32 [CX2032]  
A29010 [CX0001]  
A29010@TSOP32 [CX1002]  
A29040@PLCC32 [CX2032]  
A29040A [CX0001]  
A29040A@TSOP32 [CX1002]  
A29040B@PLCC32 [CX2032]  
A29160TG@FBGA48 [CX5002]  
A29160TV@TSOP48 [CX1004]  
A29160UM@PSOP44 [CX1014]  
A29400TM@PSOP44 [CX1014]  
A29400UM@PSOP44 [CX1014]  
A29512 [CX0001]  
A29512@TSOP32 [CX1002]  
A29512A@PLCC32 [CX2032]  
A29800TM@PSOP44 [CX1014]  
A29800UM@PSOP44 [CX1014]  
A29801TM@PSOP44 [CX1014]  
A29801UM@PSOP44 [CX1014]  
A29DL162TG@FBGA48 [CX5002]  
A29DL162UG@FBGA48 [CX5002]  
A29DL163TG@FBGA48 [CX5002]  
A29DL163UG@FBGA48 [CX5002]  
A29DL164TG@FBGA48 [CX5002]  
A29DL164UG@FBGA48 [CX5002]  
A29DL320FTV@TSOP48 [CX1004]  
A29DL322TG@FBGA48 [CX5002]  
A29DL322UG@FBGA48 [CX5002]  
A29DL323TG@FBGA48 [CX5002]  
A29DL323TV(old)@TSOP48 [CX1004]  
A29DL323UG@FBGA48 [CX5002]  
A29DL323UV(old)@TSOP48 [CX1004]  
A29DL324TG@FBGA48 [CX5002]  
A29DL324TV(old)@TSOP48 [CX1004]  
A29DL324UG@FBGA48 [CX5002]  
A29DL324UV(old)@TSOP48 [CX1004]  
A29L004ATL@PLCC32 [CX2032]  
A29L004ATW@TSOP40 [CX1006]  
A29L004AUL@PLCC32 [CX2032]  
A29L004AUW@TSOP40 [CX1006]  
A29L004T@PLCC32 [CX2032]  
A29L004T@TSOP40 [CX1006]  
A29L004U@PLCC32 [CX2032]  
A29L004U@TSOP40 [CX1006]  
A29L008ATV@TSOP40 [CX1006]  
A29L008T@TSOP40 [CX1006]  
A29L040 [CX0001]  
A29L040@TSOP32 [CX1002]  
A29L160ATG@FBGA48 [CX5002]  
A29L160ATV@TSOP48 [CX1004]  
A29L160AUM@PSOP44 [CX1014]  
A29001T@PLCC32 [CX2032]  
A29001U [CX0001]  
A29001U@TSOP32 [CX1002]  
A290021T@PLCC32 [CX2032]  
A290021U [CX0001]  
A290021U@TSOP32 [CX1002]  
A29002T@PLCC32 [CX2032]  
A29002U [CX0001]  
A29002U@TSOP32 [CX1002]  
A29010@PLCC32 [CX2032]  
A29040 [CX0001]  
A29040@TSOP32 [CX1002]  
A29040A@PLCC32 [CX2032]  
A29040B [CX0001]  
A29040B@TSOP32 [CX1002]  
A29160TM@PSOP44 [CX1014]  
A29160UG@FBGA48 [CX5002]  
A29160UV@TSOP48 [CX1004]  
A29400TV@TSOP48 [CX1004]  
A29400UV@TSOP48 [CX1004]  
A29512@PLCC32 [CX2032]  
A29512A [CX0001]  
A29512A@TSOP32 [CX1002]  
A29800TV@TSOP48 [CX1043]  
A29800UV@TSOP48 [CX1043]  
A29801TV@TSOP48 [CX1004]  
A29801UV@TSOP48 [CX1004]  
A29DL162TV@TSOP48 [CX1004]  
A29DL162UV@TSOP48 [CX1004]  
A29DL163TV@TSOP48 [CX1004]  
A29DL163UV@TSOP48 [CX1004]  
A29DL164TV@TSOP48 [CX1004]  
A29DL164UV@TSOP48 [CX1004]  
A29DL320FUV@TSOP48 [CX1004]  
A29DL322TV@TSOP48 [CX1004]  
A29DL322UV@TSOP48 [CX1004]  
A29DL323TV(old)@FBGA63 [CX5047]  
A29DL323TV@TSOP48 [CX1004]  
A29DL323UV(old)@FBGA63 [CX5047]  
A29DL323UV@TSOP48 [CX1004]  
A29DL324TV(old)@FBGA63 [CX5047]  
A29DL324TV@TSOP48 [CX1004]  
A29DL324UV(old)@FBGA63 [CX5047]  
A29DL324UV@TSOP48 [CX1004]  
A29L004ATV@TSOP32 [CX1002]  
A29L004ATY@VSOP32 [CX1003]  
A29L004AUV@TSOP32 [CX1002]  
A29L004AUY@VSOP32 [CX1003]  
A29L004T@TSOP32 [CX1002]  
A29L004T@VSOP32 [CX1003]  
A29L004U@TSOP32 [CX1002]  
A29L004U@VSOP32 [CX1003]  
A29L008AUV@TSOP40 [CX1006]  
A29L008U@TSOP40 [CX1006]  
A29L040@PLCC32 [CX2032]  
A29L040@VSOP32 [CX1003]  
A29L160ATM@PSOP44 [CX1014]  
A29L160AUG@FBGA48 [CX5002]  
A29L160AUV@TSOP48 [CX1004]

A29L160AUV@TSOP48(slow) [CX1004]      A29L160BTG@FBGA48 [CX5002]  
A29L160BTV@TSOP48 [CX1004]      A29L160BUG@FBGA48 [CX5002]  
A29L160BUV@TSOP48 [CX1004]      A29L160FTV@TSOP48 [CX1004]  
A29L160FUV@TSOP48 [CX1004]      A29L160HTG@FBGA48 [CX5002]  
A29L160HTV@TSOP48 [CX1004]      A29L160HUG@FBGA48 [CX5002]  
A29L160HUV@TSOP48 [CX1004]      A29L160TG@FBGA48 [CX5002]  
A29L160TM@PSOP44 [CX1014]      A29L160TV@TSOP48 [CX1004]  
A29L160UG@FBGA48 [CX5002]      A29L160UM@PSOP44 [CX1014]  
A29L160UV@TSOP48 [CX1004]      A29L320ATG@FBGA48 [CX5002]  
A29L320ATV@TSOP48 [CX1004]      A29L320AUG@FBGA48 [CX5002]  
A29L320AUV@TSOP48 [CX1004]      A29L400ATG@FBGA48 [CX5002]  
A29L400ATM@PSOP44 [CX1014]      A29L400ATV@TSOP48 [CX1004]  
A29L400AUG@FBGA48 [CX5002]      A29L400AUM@PSOP44 [CX1014]  
A29L400AUV@TSOP48 [CX1004]      A29L400TG@FBGA48 [CX5002]  
A29L400TM@PSOP44 [CX1014]      A29L400TV@TSOP48 [CX1004]  
A29L400UG@FBGA48 [CX5002]      A29L400UM@PSOP44 [CX1014]  
A29L400UV@TSOP48 [CX1004]      A29L800ATG@FBGA48 [CX5002]  
A29L800ATM@PSOP44 [CX1014]      A29L800ATV@TSOP48 [CX1004]  
A29L800AUG@FBGA48 [CX5002]      A29L800AUM@PSOP44 [CX1014]  
A29L800AUV@TSOP48 [CX1004]      A29L800HTG@FBGA48 [CX5002]  
A29L800HTM@PSOP44 [CX1014]      A29L800HTV@TSOP48 [CX1004]  
A29L800HUG@FBGA48 [CX5002]      A29L800HUM@PSOP44 [CX1014]  
A29L800HUV@TSOP48 [CX1004]      A29L800TG@FBGA48 [CX5002]  
A29L800TM@PSOP44 [CX1014]      A29L800TV@TSOP48 [CX1004]  
A29L800UG@FBGA48 [CX5002]      A29L800UM@PSOP44 [CX1014]  
A29L800UV@TSOP48 [CX1004]      A49LF004@PLCC32 [CX2032]  
A49LF004@VSOP32 [CX1003]      A49LF004M@PLCC32 [CX2032]  
A49LF004M@VSOP32 [CX1003]      A49LF040AT@PLCC32 [CX2032]  
A49LF040AT@VSOP32 [CX1003]      A49LF040T@PLCC32 [CX2032]  
A49LF040T@VSOP32 [CX1003]      A50FW040@PLCC32 [CX2032]  
A50FW040@VSOP32 [CX1003]      A50FW040M@PLCC32 [CX2032]  
A50FW040M@VSOP32 [CX1003]      A50LPW040@PLCC32 [CX2032]  
A50LPW040@VSOP32 [CX1003]      A617308 [CX0001]  
A617308@TSOP32 [CX0001]      A61L5308 [CX0001]  
A61L5308@TSOP28 [CX1024]      A623308(M) [CX0001]  
A623308(R)@TSOP28 [CX1024]      A623308(V)@TSOP28 [CX1024]  
A625308(M) [CX0001]      A625308(R)@TSOP28 [CX1024]  
A625308(V)@TSOP28 [CX1024]      A62L256 [CX0001]  
A62L256(M) [CX0001]      A62L256(R)@TSOP28 [CX1024]  
A62L256(V)@TSOP28 [CX1024]      A62S6308(M) [CX0001]  
A62S6308(U)@BGA48 [CX0001]      A62S6308(X)@TSOP32 [CX0001]  
A62S7308A(M) [CX0001]      A62S7308A(U)@BGA48 [CX0001]  
A62S7308A(X)@TSOP32 [CX0001]      A62S8308A(M) [CX0001]  
A62S8308A(U)@BGA48 [CX0001]      A62S8308A(X)@TSOP32 [CX0001]  
A62W5308(M) [CX0001]      A62W5308(R)@TSOP28 [CX1024]  
A62W5308(V)@TSOP28 [CX1024]      A81L801TG@FBGA69 [CX5001]  
A81L801UG@FBGA69 [CX5001]      A82DL1622TG@FBGA69 [CX5001]  
A82DL1622UG@FBGA69 [CX5001]      A82DL1624TG@FBGA69 [CX5001]  
A82DL1624UG@FBGA69 [CX5001]      A82DL1632TG@FBGA69 [CX5001]  
A82DL1632UG@FBGA69 [CX5001]      A82DL1634TG@FBGA69 [CX5001]  
A82DL1634UG@FBGA69 [CX5001]      A82DL1642TG@FBGA69 [CX5001]  
A82DL1642UG@FBGA69 [CX5001]      A82DL1644TG@FBGA69 [CX5001]  
A82DL1644UG@FBGA69 [CX5001]      A82DL32216TG@FBGA69 [CX5001]  
A82DL32216UG@FBGA69 [CX5001]      A82DL3224TG@FBGA69 [CX5001]  
A82DL3224UG@FBGA69 [CX5001]      A82DL3228TG@FBGA69 [CX5001]  
A82DL3228UG@FBGA69 [CX5001]      A82DL32316TG@FBGA69 [CX5001]  
A82DL32316UG@FBGA69 [CX5001]      A82DL3234TG@FBGA69 [CX5001]  
A82DL3234UG@FBGA69 [CX5001]      A82DL3238TG@FBGA69 [CX5001]  
A82DL3238UG@FBGA69 [CX5001]      A82DL32416TG@FBGA69 [CX5001]

A82DL32416UG@FBGA69 [CX5001]  
A82DL3244UG@FBGA69 [CX5001]  
A82DL3248UG@FBGA69 [CX5001]

A82DL3244TG@FBGA69 [CX5001]  
A82DL3248TG@FBGA69 [CX5001]

## AMS

### MICROCONTROLLER

AS5030 [CX1001]  
AS5032 [CX1001]  
AS5034 [CX1001]

AS5031 [CX1001]  
AS5033 [CX1001]  
AS5035 [CX1001]

## ANACHIP

### E (E) PROM/FRAM/NVRAM

27CX010 [CX0001]  
27CX010@TSOP32 [CX1002]  
27CX321 [CX0001]  
27CX641 [CX0001]  
93C46 [CX0001]  
93C46A [CX0001]  
93C56A [CX0001]  
93C66A [CX0001]  
93CX46 [CX0001]  
93CX56 [CX0001]  
93CX66 [CX0001]  
AM24LC02 [CX0001]  
AM24LC02@TSSOP8 [CX1059]  
AM24LC04@SOIC8 [CX1045]  
AM24LC08 [CX0001]  
AM24LC08@TSSOP8 [CX1059]  
AM24LC16@SOIC8 [CX1045]  
AM24LC21 [CX0001]  
AM24LC21@TSSOP8 [CX1059]  
AM24LC21B@SOIC8 [CX1045]  
AM93LC46(08bit) [CX0001]  
AM93LC46(08bit)@TSOP8 [CX1059]  
AM93LC46(16bit)@SOIC8 [CX1045]  
AM93LC56(08bit) [CX0001]  
AM93LC56(08bit)@TSOP8 [CX1059]  
AM93LC56(16bit)@SOIC8 [CX1045]  
AM93LC66(08bit) [CX0001]  
AM93LC66(08bit)@TSOP8 [CX1059]  
AM93LC66(16bit)@SOIC8 [CX1045]  
AM93LC86(08bit) [CX0001]  
AM93LC86(08bit)@TSOP8 [CX1059]  
AM93LC86(16bit)@SOIC8 [CX1045]

27CX010@PLCC32 [CX2032]  
27CX256 [CX0001]  
27CX322 [CX0001]  
27CX642 [CX0001]  
93C46@SOIC8 [CX1045]  
93C46A@SOIC8 [CX1045]  
93C56A@SOIC8 [CX1045]  
93C66A@SOIC8 [CX1045]  
93CX46@SOIC8 [CX1045]  
93CX56@SOIC8 [CX1045]  
93CX66@SOIC8 [CX1045]  
AM24LC02@SOIC8 [CX1045]  
AM24LC04 [CX0001]  
AM24LC04@TSSOP8 [CX1059]  
AM24LC08@SOIC8 [CX1045]  
AM24LC16 [CX0001]  
AM24LC16@TSSOP8 [CX1059]  
AM24LC21@SOIC8 [CX1045]  
AM24LC21B [CX0001]  
AM24LC21B@TSSOP8 [CX1059]  
AM93LC46(08bit)@SOIC8 [CX1045]  
AM93LC46(16bit) [CX0001]  
AM93LC46(16bit)@TSOP8 [CX1059]  
AM93LC56(08bit)@SOIC8 [CX1045]  
AM93LC56(16bit) [CX0001]  
AM93LC56(16bit)@TSOP8 [CX1059]  
AM93LC66(08bit)@SOIC8 [CX1045]  
AM93LC66(16bit) [CX0001]  
AM93LC66(16bit)@TSOP8 [CX1059]  
AM93LC86(08bit)@SOIC8 [CX1045]  
AM93LC86(16bit) [CX0001]  
AM93LC86(16bit)@TSOP8 [CX1059]

### PLD

PA7024 [CX0001]  
PA7024(JN)@PLCC28 [CX2028]  
PA7140 [CX0001]  
PA7140@TQFP44 [CX3003]  
PA7540(J)@PLCC28 [CX2028]

PA7024(J)@PLCC28 [CX2028]  
PA7024@SOIC24 [CX1033]  
PA7140@PLCC44 [CX2044]  
PA7540 [CX0001]  
PA7540(JN)@PLCC28 [CX2028]

PA7572 [CX0001]  
PA7572@TQFP44 [CX3003]  
PEEL18CV8P [CX0001]  
PEEL18CV8T@TSOP20 [CX1000]  
PEEL18CV8Z@PLCC20 [CX2020]  
PEEL18CV8Z@TSOP20 [CX1000]  
PEEL18LV8Z@PLCC20 [CX2020]  
PEEL18LV8Z@TSOP20 [CX1000]  
PEEL22CV10A@PLCC28 [CX2028]  
PEEL22CV10A@TSOP24 [CX1000]  
PEEL22CV10A+@PLCC28 [CX2028]  
PEEL22CV10A+@TSOP24 [CX1000]  
PEEL22CV10A++@PLCC28 [CX2028]  
PEEL22CV10A++@TSOP24 [CX1000]  
PEEL22CV10AZ@PLCC28 [CX2028]  
PEEL22CV10AZ@TSOP24 [CX1000]  
PEEL22CV10AZ+@PLCC28 [CX2028]  
PEEL22CV10AZ+@TSOP24 [CX1000]  
PEEL22CV10AZ++@PLCC28 [CX2028]  
PEEL22CV10AZ++@TSOP24 [CX1000]  
PEEL22LV10AZ@PLCC28 [CX2028]  
PEEL22LV10AZ@TSOP24 [CX1000]  
PEEL22LV10AZ+@PLCC28 [CX2028]  
PEEL22LV10AZ+@TSOP24 [CX1000]  
PEEL22LV10AZ++@PLCC28 [CX2028]  
PEEL22LV10AZ++@TSOP24 [CX1000]

PA7572@PLCC44 [CX2044]  
PEEL18CV8J@PLCC20 [CX2020]  
PEEL18CV8S@SOIC20 [CX1033]  
PEEL18CV8Z [CX0001]  
PEEL18CV8Z@SOIC20 [CX1033]  
PEEL18LV8Z [CX0001]  
PEEL18LV8Z@SOIC20 [CX1033]  
PEEL22CV10A [CX0001]  
PEEL22CV10A@SOIC24 [CX1033]  
PEEL22CV10A+ [CX0001]  
PEEL22CV10A+@SOIC24 [CX1033]  
PEEL22CV10A++ [CX0001]  
PEEL22CV10A++@SOIC24 [CX1033]  
PEEL22CV10AZ [CX0001]  
PEEL22CV10AZ@SOIC24 [CX1033]  
PEEL22CV10AZ+ [CX0001]  
PEEL22CV10AZ+@SOIC24 [CX1033]  
PEEL22CV10AZ++ [CX0001]  
PEEL22CV10AZ++@SOIC24 [CX1033]  
PEEL22LV10AZ [CX0001]  
PEEL22LV10AZ@SOIC24 [CX1033]  
PEEL22LV10AZ+ [CX0001]  
PEEL22LV10AZ+@SOIC24 [CX1033]  
PEEL22LV10AZ++ [CX0001]  
PEEL22LV10AZ++@SOIC24 [CX1033]

## APLUS FLASH

### E (E) PROM/FRAM/NVRAM

AF24BC01 [CX0001]  
AF24BC01@TSSOP8 [CX1059]  
AF24BC02@SOIC8 [CX1045]  
AF24BC04 [CX0001]  
AF24BC04@TSSOP8 [CX1059]  
AF24BC08@SOIC8 [CX1045]  
AF24BC128 [CX0001]  
AF24BC128@TSOP8 [CX1059]  
AF24BC16@SOIC8 [CX1045]  
AF24BC256 [CX0001]  
AF24BC256@TSOP8 [CX1059]  
AF24BC32@SOIC8 [CX1045]  
AF24BC64 [CX0001]  
AF24BC64@TSOP8 [CX1059]  
AF24C128@SOIC8 [CX1045]  
AF24C256 [CX0001]  
AF24C256@TSOP8 [CX1059]  
AF24C32@SOIC8 [CX1045]  
AF24C64 [CX0001]  
AF24C64@TSOP8 [CX1059]  
AF25BC08@SOIC8 [CX1045]  
AF25BC128 [CX0001]  
AF25BC128@TSOP8 [CX1059#1]  
AF25BC16@SOIC8 [CX1045]  
AF25BC256 [CX0001]  
AF25BC256@TSOP8 [CX1059#1]  
AF25BC32@SOIC8 [CX1045]

AF24BC01@SOIC8 [CX1045]  
AF24BC02 [CX0001]  
AF24BC02@TSSOP8 [CX1059]  
AF24BC04@SOIC8 [CX1045]  
AF24BC08 [CX0001]  
AF24BC08@TSSOP8 [CX1059]  
AF24BC128@SOIC8 [CX1045]  
AF24BC16 [CX0001]  
AF24BC16@TSSOP8 [CX1059]  
AF24BC256@SOIC8 [CX1045]  
AF24BC32 [CX0001]  
AF24BC32@TSOP8 [CX1059]  
AF24BC64@SOIC8 [CX1045]  
AF24C128 [CX0001]  
AF24C128@TSOP8 [CX1059]  
AF24C256@SOIC8 [CX1045]  
AF24C32 [CX0001]  
AF24C32@TSOP8 [CX1059]  
AF24C64@SOIC8 [CX1045]  
AF25BC08 [CX0001]  
AF25BC08@TSOP8 [CX1059]  
AF25BC128@SOIC8 [CX1045#1]  
AF25BC16 [CX0001]  
AF25BC16@TSOP8 [CX1059]  
AF25BC256@SOIC8 [CX1045#1]  
AF25BC32 [CX0001]  
AF25BC32@TSOP8 [CX1059]

AF25BC64 [CX0001]  
AF25BC64@TSOP8 [CX1059]  
AF93BC46(08bit)@SOIC8 [CX1045]  
AF93BC46(16bit) [CX0001]  
AF93BC46(16bit)@TSOP8 [CX1059]  
AF93BC56(08bit)@SOIC8 [CX1045]  
AF93BC56(16bit) [CX0001]  
AF93BC56(16bit)@TSOP8 [CX1059]  
AF93BC66(08bit)@SOIC8 [CX1045]  
AF93BC66(16bit) [CX0001]  
AF93BC66(16bit)@TSOP8 [CX1059]  
AF93BC86(08bit)@SOIC8 [CX1045]  
AF93BC86(16bit) [CX0001]  
AF93BC86(16bit)@TSOP8 [CX1059]  
AF93C46(08bit)@SOIC8 [CX1045]  
AF93C46(16bit) [CX0001]  
AF93C46(16bit)@TSOP8 [CX1059]  
AF93C56(08bit)@SOIC8 [CX1045]  
AF93C56(16bit) [CX0001]  
AF93C56(16bit)@TSOP8 [CX1059]  
AF93C66(08bit)@SOIC8 [CX1045]  
AF93C66(16bit) [CX0001]  
AF93C66(16bit)@TSOP8 [CX1059]  
AF93C86(08bit)@SOIC8 [CX1045]  
AF93C86(16bit) [CX0001]  
AF93C86(16bit)@TSOP8 [CX1059]

AF25BC64@SOIC8 [CX1045]  
AF93BC46(08bit) [CX0001]  
AF93BC46(08bit)@TSOP8 [CX1059]  
AF93BC46(16bit)@SOIC8 [CX1045]  
AF93BC56(08bit) [CX0001]  
AF93BC56(08bit)@TSOP8 [CX1059]  
AF93BC56(16bit)@SOIC8 [CX1045]  
AF93BC66(08bit) [CX0001]  
AF93BC66(08bit)@TSOP8 [CX1059]  
AF93BC66(16bit)@SOIC8 [CX1045]  
AF93BC86(08bit) [CX0001]  
AF93BC86(08bit)@TSOP8 [CX1059]  
AF93BC86(16bit)@SOIC8 [CX1045]  
AF93C46(08bit) [CX0001]  
AF93C46(08bit)@TSOP8 [CX1059]  
AF93C46(16bit)@SOIC8 [CX1045]  
AF93C56(08bit) [CX0001]  
AF93C56(08bit)@TSOP8 [CX1059]  
AF93C56(16bit)@SOIC8 [CX1045]  
AF93C66(08bit) [CX0001]  
AF93C66(08bit)@TSOP8 [CX1059]  
AF93C66(16bit)@SOIC8 [CX1045]  
AF93C86(08bit) [CX0001]  
AF93C86(08bit)@TSOP8 [CX1059]  
AF93C86(16bit)@SOIC8 [CX1045]

## ARTSCHIP

### E (E) PROM/FRAM/NVRAM

24AA02 [CX0001]  
24AA02@MSOP8 [CX1015]  
24AA02@SOT5 [CX1041]  
24LC01A [CX0001]  
24LC01A@MAP8  
24LC01A@SOT5 [CX1041]  
24LC01B [CX0001]  
24LC01B@SOT5 [CX1041]  
24LC02A [CX0001]  
24LC02A@MAP8  
24LC02A@SOT5 [CX1041]  
24LC02B [CX0001]  
24LC02B@MSOP8 [CX1015]  
24LC02B@SOT5 [CX1041]  
24LC04A [CX0001]  
24LC04A@MAP8  
24LC04A@SOT5 [CX1041]  
24LC04B [CX0001]  
24LC04B@MSOP8 [CX1015]  
24LC04B@SOT5 [CX1041]  
24LC08A [CX0001]  
24LC08A@MAP8  
24LC08A@SOT5 [CX1041]  
24LC08B [CX0001]  
24LC08B@MSOP8 [CX1015]  
24LC08B@SOT5 [CX1041]  
24LC16A [CX0001]

24AA02@DFN8 [CX4002]  
24AA02@SOIC8 [CX1045]  
24AA02@TSSOP8 [CX1059]  
24LC01A@dBG8  
24LC01A@SOIC8 [CX1045]  
24LC01A@TSSOP8 [CX1059]  
24LC01B@SOIC8 [CX1045]  
24LC01B@TSSOP8 [CX1059]  
24LC02A@dBG8  
24LC02A@SOIC8 [CX1045]  
24LC02A@TSSOP8 [CX1059]  
24LC02B@DFN8 [CX4002]  
24LC02B@SOIC8 [CX1045]  
24LC02B@TSSOP8 [CX1059]  
24LC04A@dBG8  
24LC04A@SOIC8 [CX1045]  
24LC04A@TSSOP8 [CX1059]  
24LC04B@DFN8 [CX4002]  
24LC04B@SOIC8 [CX1045]  
24LC04B@TSSOP8 [CX1059]  
24LC08A@dBG8  
24LC08A@SOIC8 [CX1045]  
24LC08A@TSSOP8 [CX1059]  
24LC08B@DFN8 [CX4002]  
24LC08B@SOIC8 [CX1045]  
24LC08B@TSSOP8 [CX1059]  
24LC16A@dBG8

24LC16A@MAP8  
24LC16A@SOT5 [CX1041]  
24LC256B [CX0001]  
24LC256B@SOIC8 [CX1045]  
24LC32 [CX0001]  
24LC32@SOIC8 [CX1045]  
24LC64 [CX0001]  
24LC64@SOIC8 [CX1045]

24LC16A@SOIC8 [CX1045]  
24LC16A@TSSOP8 [CX1059]  
24LC256B@MSOP8 [CX1015]  
24LC256B@TSSOP8 [CX1059]  
24LC32@SOIC14 [CX1000]  
24LC32@TSSOP8 [CX1059]  
24LC64@SOIC14 [CX1000]  
24LC64@TSSOP8 [CX1059]

## ASAHI KASEI(AKM)

### E (E) PROM/FRAM/NVRAM

AK27CX321 [CX0001]  
AK27CX641 [CX0001]  
AK6002A(F)@SOP8 [CX1045]  
AK6003A(V)@TSSOP8 [CX1059]  
AK6004A(M)@SSOP8 [CX1044]  
AK6010A(F)@SOP8 [CX1045]  
AK6416A(M)@SSOP8 [CX1000]  
AK6420A(F)@SOP8 [CX1045]  
AK6420B(H)@MSOP8 [CX1015]  
AK6440A(M)@SSOP8 [CX1000]  
AK6480A(F)@SOP8 [CX1045]  
AK6480B(H)@MSOP8 [CX1015]  
AK6480C(H)@MSOP8 [CX1015]  
AK6480C(M)@SSOP8 [CX1000]  
AK6481C(M)@SSOP8 [CX1000]  
AK6508C(U)@USON8 [CX0001]  
AK6510C(M)@SSOP8 [CX1059]  
AK6512C(M)@SSOP8 [CX1059]  
AK6514C(N)@QFN20 [CX4011]  
AK93C10A(F)@SOP8 [CX1045]  
AK93C45 [CX0001]  
AK93C45A(F)@SOP8 [CX1045]  
AK93C45A(V)@TSSOP8 [CX1059]  
AK93C45B(L)@SON8 [CX5156]  
AK93C45C(U)@USON8 [CX5156]  
AK93C45L(F)@SOP8 [CX1045]  
AK93C46(F)@SOP8 [CX1045]  
AK93C46A(NF)@SOP8 [CX1045]  
AK93C46B(H)@MSOP8 [CX1015]  
AK93C46C(T)@MSOP8 [CX1015]  
AK93C46L [CX0001]  
AK93C51A(V)@TSSOP8 [CX1059]  
AK93C55(F)@SOP8 [CX1045]  
AK93C55A(NF)@SOP8 [CX1045]  
AK93C55B(H)@MSOP8 [CX1015]  
AK93C55C(T)@MSOP8 [CX1015]  
AK93C55L [CX0001]  
AK93C56 [CX0001]  
AK93C56A(F)@SOP8 [CX1045]  
AK93C56A(V)@TSSOP8 [CX1059]  
AK93C56B(L)@SON8 [CX5156]  
AK93C56C(U)@USON8 [CX5156]  
AK93C56L(F)@SOP8 [CX1045]  
AK93C65 [CX0001]  
AK93C65A(F)@SOP8 [CX1045]

AK27CX322 [CX0001]  
AK27CX642 [CX0001]  
AK6002A(V)@TSSOP8 [CX1059]  
AK6004A(F)@SOP8 [CX1045]  
AK6008A(F)@SOP8 [CX1045]  
AK6012A(F)@SOP8 [CX1045]  
AK6416C(F)@SOP8 [CX1045]  
AK6420A(M)@SSOP8 [CX1000]  
AK6440A(F)@SOP8 [CX1045]  
AK6440B(H)@MSOP8 [CX1015]  
AK6480A(M)@SSOP8 [CX1000]  
AK6480C(F)@SOP8 [CX1045]  
AK6480C(L)@SON8 [CX0001]  
AK6481C(H)@MSOP8 [CX1015]  
AK6508C(T)@MSOP8 [CX1015]  
AK6510C(L)@SONW8 [CX0001]  
AK6512C(L)@SONW8 [CX0001]  
AK6514C(F)@SOP8 [CX1016]  
AK6516C(F)@SOP8 [CX1016]  
AK93C41A(V)@TSSOP8 [CX1059]  
AK93C45(F)@SOP8 [CX1045]  
AK93C45A(NF)@SOP8 [CX1045]  
AK93C45B(H)@MSOP8 [CX1015]  
AK93C45C(T)@MSOP8 [CX1015]  
AK93C45L [CX0001]  
AK93C46 [CX0001]  
AK93C46A(F)@SOP8 [CX1045]  
AK93C46A(V)@TSSOP8 [CX1059]  
AK93C46B(L)@SON8 [CX5156]  
AK93C46C(U)@USON8 [CX5156]  
AK93C46L(F)@SOP8 [CX1045]  
AK93C55 [CX0001]  
AK93C55A(F)@SOP8 [CX1045]  
AK93C55A(V)@TSSOP8 [CX1059]  
AK93C55B(L)@SON8 [CX5156]  
AK93C55C(U)@USON8 [CX5156]  
AK93C55L(F)@SOP8 [CX1045]  
AK93C56(F)@SOP8 [CX1045]  
AK93C56A(NF)@SOP8 [CX1045]  
AK93C56B(H)@MSOP8 [CX1015]  
AK93C56C(T)@MSOP8 [CX1015]  
AK93C56L [CX0001]  
AK93C61A(V)@TSSOP8 [CX1059]  
AK93C65(F)@SOP8 [CX1045]  
AK93C65A(NF)@SOP8 [CX1045]



AK93C65A(V)@TSSOP8 [CX1059]  
AK93C65B(L)@SON8 [CX5156]  
AK93C65C(U)@USON8 [CX5156]  
AK93C65L(F)@SOP8 [CX1045]  
AK93C66(F)@SOP8 [CX1045]  
AK93C66A(NF)@SOP8 [CX1045]  
AK93C66B(H)@MSOP8 [CX1015]  
AK93C66C(T)@MSOP8 [CX1015]  
AK93C66L [CX0001]  
AK93C75 [CX0001]  
AK93C75A(F)@SOP8 [CX1045]  
AK93C75A(V)@TSSOP8 [CX1059]  
AK93C75L [CX0001]  
AK93C85 [CX0001]  
AK93C85L [CX0001]  
AK93C95A(F)@SOP8 [CX1045]  
AK9824(M)@SSOP8 [CX1000]

AK93C65B(H)@MSOP8 [CX1015]  
AK93C65C(T)@MSOP8 [CX1015]  
AK93C65L [CX0001]  
AK93C66 [CX0001]  
AK93C66A(F)@SOP8 [CX1045]  
AK93C66A(V)@TSSOP8 [CX1059]  
AK93C66B(L)@SON8 [CX5156]  
AK93C66C(U)@USON8 [CX5156]  
AK93C66L(F)@SOP8 [CX1045]  
AK93C75(F)@SOP8 [CX1045]  
AK93C75A(NF)@SOP8 [CX1045]  
AK93C75B(H)@MSOP8 [CX1015]  
AK93C75L(F)@SOP8 [CX1045]  
AK93C85(F)@SOP8 [CX1045]  
AK93C85L(F)@SOP8 [CX1045]  
AK9822(M)@SSOP8 [CX1000]  
AK9844@SOIC14 [CX1016]

## ASD

### E (E) PROM/FRAM/NVRAM

AE29F1008 [CX0001]

AE29F2008 [CX0001]

## ASI

### E (E) PROM/FRAM/NVRAM

AS58C1001 [CX0001]  
AS58C1001@SSOP32 [CX1020]

AS58C1001@PLCC32 [CX2032]

## Asic Microelectronics

### E (E) PROM/FRAM/NVRAM

AX24C02@SOP8 [CX1045]  
AX24C08@SOP8 [CX1045]

AX24C04@SOP8 [CX1045]  
AX24C16@SOP8 [CX1045]

## ASP

### MICROCONTROLLER

AP827C51 [CX0001]  
AP827C52 [CX0001]  
AP827C54 [CX0001]  
AP827C58 [CX0001]

AP827C51@PLCC44 [CX2044]  
AP827C52@PLCC44 [CX2044]  
AP827C54@PLCC44 [CX2044]  
AP827C58@PLCC44 [CX2044]

## ASTIGP-MICROCHIP

### MICROCONTROLLER

PIC16F616 [CX0001]  
PIC16F616@SOIC14 [CX1016]

PIC16F616@QFN16 [CX4010]  
PIC16F616@TSSOP14 [CX1000]

# ATC

## E (E) PROM/FRAM/NVRAM

ATC24C02 [CX0001]	ATC24C02@SOIC8 [CX1045]
ATC24C02@TSSOP8 [CX1059]	ATC24C04 [CX0001]
ATC24C04@SOIC8 [CX1045]	ATC24C04@TSSOP8 [CX1059]
ATC24C08 [CX0001]	ATC24C08@SOIC8 [CX1045]
ATC24C08@TSSOP8 [CX1059]	ATC24C16 [CX0001]
ATC24C16@SOIC8 [CX1045]	ATC24C16@TSSOP8 [CX1059]
ATC24LC02 [CX0001]	ATC24LC02@SOIC8 [CX1045]
ATC24LC02@TSSOP8 [CX1059]	ATC24LC02A [CX0001]
ATC24LC02A@SOIC8 [CX1045]	ATC24LC02A@TSSOP8 [CX1059]
ATC24LC04 [CX0001]	ATC24LC04@SOIC8 [CX1045]
ATC24LC04@TSSOP8 [CX1059]	ATC24LC08 [CX0001]
ATC24LC08@SOIC8 [CX1045]	ATC24LC08@TSSOP8 [CX1059]
ATC24LC16 [CX0001]	ATC24LC16@SOIC8 [CX1045]
ATC24LC16@TSSOP8 [CX1059]	ATC93C46(08bit) [CX0001]
ATC93C46(08bit)@SOIC8 [CX1045]	ATC93C46(16bit) [CX0001]
ATC93C46(16bit)@SOIC8 [CX1045]	ATC93C46R(08bit)@SOIC8 [CX1045]
ATC93C46R(16bit)@SOIC8 [CX1045]	ATC93C56(08bit) [CX0001]
ATC93C56(08bit)@SOIC8 [CX1045]	ATC93C56(16bit) [CX0001]
ATC93C56(16bit)@SOIC8 [CX1045]	ATC93C56R(08bit)@SOIC8 [CX1045]
ATC93C56R(16bit)@SOIC8 [CX1045]	ATC93C66(08bit) [CX0001]
ATC93C66(08bit)@SOIC8 [CX1045]	ATC93C66(16bit) [CX0001]
ATC93C66(16bit)@SOIC8 [CX1045]	ATC93C66R(08bit)@SOIC8 [CX1045]
ATC93C66R(16bit)@SOIC8 [CX1045]	ATC93LC46(08bit) [CX0001]
ATC93LC46(08bit)@SOIC8 [CX1045]	ATC93LC46(16bit) [CX0001]
ATC93LC46(16bit)@SOIC8 [CX1045]	ATC93LC46R(08bit)@SOIC8 [CX1045]
ATC93LC46R(16bit)@SOIC8 [CX1045]	ATC93LC56(08bit) [CX0001]
ATC93LC56(08bit)@SOIC8 [CX1045]	ATC93LC56(16bit) [CX0001]
ATC93LC56(16bit)@SOIC8 [CX1045]	ATC93LC56R(08bit)@SOIC8 [CX1045]
ATC93LC56R(16bit)@SOIC8 [CX1045]	ATC93LC66(08bit) [CX0001]
ATC93LC66(08bit)@SOIC8 [CX1045]	ATC93LC66(16bit) [CX0001]
ATC93LC66(16bit)@SOIC8 [CX1045]	ATC93LC66R(08bit)@SOIC8 [CX1045]
ATC93LC66R(16bit)@SOIC8 [CX1045]	

# ATMEL

## E (E) PROM/FRAM/NVRAM

AT17C002@PLCC20 [CX2020]	AT17C002@PLCC44 [CX2044]
AT17C002@SOIC20 [CX1033]	AT17C002@TQFP44 [CX3005]
AT17C002A@PLCC20 [CX2020]	AT17C002A@TQFP32 [CX3001]
AT17C010 [CX0001]	AT17C010@PLCC20 [CX2020]
AT17C010A [CX0001]	AT17C010A@PLCC20 [CX2020]
AT17C020@PLCC20 [CX2020]	AT17C020A@PLCC20 [CX2020]
AT17C040@PLCC44 [CX2044]	AT17C040@TQFP44 [CX3005]
AT17C128 [CX0001]	AT17C128@PLCC20 [CX2020]
AT17C128@SOIC20 [CX1033]	AT17C128@SOIC8 [CX1045]
AT17C128A@PLCC20 [CX2020]	AT17C256 [CX0001]
AT17C256@PLCC20 [CX2020]	AT17C256@SOIC20 [CX1033]
AT17C256@SOIC8 [CX1045]	AT17C256A@PLCC20 [CX2020]
AT17C512 [CX0001]	AT17C512@PLCC20 [CX2020]
AT17C512A [CX0001]	AT17C512A@PLCC20 [CX2020]
AT17C65 [CX0001]	AT17C65@PLCC20 [CX2020]
AT17C65@SOIC20 [CX1033]	AT17C65@SOIC8 [CX1045]

AT17C65A@PLCC20 [CX2020] AT17F040@LAP8 [CX4024]  
AT17F040@PLCC20 [CX2020]  
AT17F040@PLCC20(Virtex Pinout) [CX2020]  
AT17F040A@LAP8 [CX4024] AT17F040A@PLCC20 [CX2020]  
AT17F040A@TQFP32 [CX3001] AT17F080@LAP8 [CX4024]  
AT17F080@PLCC20 [CX2020] AT17F080@PLCC44 [CX2044]  
AT17F080@TQFP44 [CX3005] AT17F080A@LAP8 [CX4024]  
AT17F080A@PLCC20 [CX2020] AT17F080A@TQFP32 [CX3001]  
AT17F16@LAP8 [CX4024] AT17F16@PLCC20 [CX2020]  
AT17F16@PLCC44 [CX2044] AT17F16@TQFP44 [CX3005]  
AT17F16A@LAP8 [CX4024] AT17F16A@PLCC20 [CX2020]  
AT17F32@PLCC44 [CX2044] AT17F32A@PLCC44 [CX2044]  
AT17LV002@PLCC20 [CX2020] AT17LV002@PLCC44 [CX2044]  
AT17LV002@SOIC20 [CX1033] AT17LV002@TQFP44 [CX3005]  
AT17LV002A@PLCC20 [CX2020] AT17LV002A@TQFP32 [CX3001]  
AT17LV010 [CX0001] AT17LV010@PLCC20 [CX2020]  
AT17LV010A [CX0001] AT17LV010A@PLCC20 [CX2020]  
AT17LV020@PLCC20 [CX2020] AT17LV020A@PLCC20 [CX2020]  
AT17LV040@PLCC44 [CX2044] AT17LV040@TQFP44 [CX3005]  
AT17LV128 [CX0001] AT17LV128@PLCC20 [CX2020]  
AT17LV128@SOIC20 [CX1033] AT17LV128@SOIC8 [CX1045]  
AT17LV128A@PLCC20 [CX2020] AT17LV256 [CX0001]  
AT17LV256@PLCC20 [CX2020] AT17LV256@SOIC20 [CX1033]  
AT17LV256@SOIC8 [CX1045] AT17LV256A@PLCC20 [CX2020]  
AT17LV512 [CX0001] AT17LV512@PLCC20 [CX2020]  
AT17LV512A [CX0001] AT17LV512A@PLCC20 [CX2020]  
AT17LV65 [CX0001] AT17LV65@PLCC20 [CX2020]  
AT17LV65@SOIC20 [CX1033] AT17LV65@SOIC8 [CX1045]  
AT17LV65A@PLCC20 [CX2020] AT17N002@SOIC20 [CX1033]  
AT17N002@TQFP44 [CX3005] AT17N010 [CX0001]  
AT17N010@SOIC20 [CX1033] AT17N040@TQFP44 [CX3005]  
AT17N256 [CX0001] AT17N256@SOIC20 [CX1033]  
AT17N256@SOIC8 [CX1045] AT17N512 [CX0001]  
AT17N512@SOIC20 [CX1033] AT24C01 [CX0001]  
AT24C01@MSOP8 [CX1015] AT24C01@SOIC8 [CX1045]  
AT24C01@TSSOP8 [CX1059] AT24C01A [CX0001]  
AT24C01A@MAP8 [CX4002] AT24C01A@SOIC8 [CX1045]  
AT24C01A@SOT23-5 [CX1041] AT24C01A@TSSOP8 [CX1059]  
AT24C01B [CX0001] AT24C01B@dBGA2 [CX5156]  
AT24C01B@MAP8 [CX4002] AT24C01B@SOIC8 [CX1045]  
AT24C01B@SOT23 [CX1041] AT24C01B@TSSOP8 [CX1059]  
AT24C01C [CX0001] AT24C01C@dBGA8 [CX5156]  
AT24C01C@MAP8 [CX4002] AT24C01C@SOIC8 [CX1045]  
AT24C01C@SOT23 [CX1041] AT24C01C@TSSOP8 [CX1059]  
AT24C02 [CX0001] AT24C02@SOIC8 [CX1045]  
AT24C02@TSSOP8 [CX1059] AT24C02A [CX0001]  
AT24C02A@SOIC8 [CX1045] AT24C02A@TSSOP8 [CX1059]  
AT24C02B [CX0001] AT24C02B(HAIER) [CX0001]  
AT24C02B@dBGA2 [CX5156] AT24C02B@MAP8 [CX4002]  
AT24C02B@SOIC8 [CX1045] AT24C02B@SOT23 [CX1041]  
AT24C02B@TSSOP8 [CX1059] AT24C02C [CX0001]  
AT24C02C@dBGA8 [CX5156] AT24C02C@SOIC8 [CX1045]  
AT24C02C@SOT23 [CX1041] AT24C02C@TSSOP8 [CX1059]  
AT24C02C@UDFN8 [CX4002] AT24C04 [CX0001]  
AT24C04@MAP8 [CX4002] AT24C04@SOIC8 [CX1045]  
AT24C04@SOT23-5 [CX1041] AT24C04@TSSOP8 [CX1059]  
AT24C04A [CX0001] AT24C04A@MAP8 [CX4002]  
AT24C04A@SOIC8 [CX1045] AT24C04A@TSSOP8 [CX1059]  
AT24C04B [CX0001] AT24C04B@dBGA2 [CX5156]

AT24C04B@MAP8 [CX4002] AT24C04B@SOIC8 [CX1045]  
AT24C04B@SOT23 [CX1041] AT24C04B@TSSOP8 [CX1059]  
AT24C04C [CX0001] AT24C04C@dBGA8 [CX5156]  
AT24C04C@SOIC8 [CX1045] AT24C04C@SOT23 [CX1041]  
AT24C04C@TSSOP8 [CX1059] AT24C04C@UDFN8 [CX4002]  
AT24C08 [CX0001] AT24C08@MAP8 [CX4002]  
AT24C08@SOIC8 [CX1045] AT24C08@TSSOP8 [CX1059]  
AT24C08A [CX0001] AT24C08A@MAP8 [CX4002]  
AT24C08A@SOIC8 [CX1045] AT24C08A@TSSOP8 [CX1059]  
AT24C08B [CX0001] AT24C08B@dBGA2 [CX5156]  
AT24C08B@MAP8 [CX4002] AT24C08B@SOIC8 [CX1045]  
AT24C08B@SOT23 [CX1041] AT24C08B@TSSOP8 [CX1059]  
AT24C08C [CX0001] AT24C08C@dBGA8 [CX5156]  
AT24C08C@SOIC8 [CX1045] AT24C08C@SOT23 [CX1041]  
AT24C08C@TSSOP8 [CX1059] AT24C08C@UDFN8 [CX4002]  
AT24C1024 [CX0001] AT24C1024@LAP8 [CX4006]  
AT24C1024@SAP8 [CX4005] AT24C1024@SOIC8 [CX1044]  
AT24C1024B(1.8V) [CX0001] AT24C1024B(1.8V)@LAP8 [CX4006]  
AT24C1024B(1.8V)@SAP8 [CX4005]  
AT24C1024B(1.8V)@SOIC8(150mil) [CX1045]  
AT24C1024B(1.8V)@SOIC8(200mil) [CX1044]  
AT24C1024B(1.8V)@TSSOP8 [CX1059] AT24C1024B(2.5V) [CX0001]  
AT24C1024B(2.5V)@LAP8 [CX4006] AT24C1024B(2.5V)@SAP8 [CX4005]  
AT24C1024B(2.5V)@SOIC8(150mil) [CX1045]  
AT24C1024B(2.5V)@SOIC8(200mil) [CX1044]  
AT24C1024B(2.5V)@TSSOP8 [CX1059] AT24C11 [CX0001]  
AT24C11@SOIC8 [CX1045] AT24C11@TSSOP8 [CX1059]  
AT24C128(1.8V) [CX0001] AT24C128(1.8V)@MAP8 [CX4002]  
AT24C128(1.8V)@SAP8 [CX4005] AT24C128(1.8V)@SOIC8 [CX1045]  
AT24C128(1.8V)@TSSOP8 [CX1059] AT24C128(2.7V) [CX0001]  
AT24C128(2.7V)@MAP8 [CX4002] AT24C128(2.7V)@SAP8 [CX4005]  
AT24C128(2.7V)@SOIC8 [CX1045] AT24C128(2.7V)@TSSOP8 [CX1059]  
AT24C128B [CX0001] AT24C128B@MAP8 [CX4002]  
AT24C128B@SAP8 [CX4005] AT24C128B@SOIC8 [CX1045]  
AT24C128B@TSSOP8 [CX1059] AT24C128C@SOIC8 [CX1045]  
AT24C128C@TSSOP8 [CX1059] AT24C128C@UDFN8 [CX4002]  
AT24C128C@VFBGA8 [CX5156] AT24C128C@XDFN8 [CX0001]  
AT24C16 [CX0001] AT24C16@SOIC8 [CX1045]  
AT24C16@TSSOP8 [CX1059] AT24C164 [CX0001]  
AT24C164@SOIC8 [CX1045] AT24C16A [CX0001]  
AT24C16A@MAP8 [CX4002] AT24C16A@SOIC8 [CX1045]  
AT24C16A@TSSOP8 [CX1059] AT24C16B [CX0001]  
AT24C16B@MAP8 [CX4002] AT24C16B@SOIC8 [CX1045]  
AT24C16B@TSSOP8 [CX1059] AT24C21 [CX4002]  
AT24C21@SOIC8 [CX1045] AT24C256(1.8V) [CX0001]  
AT24C256(1.8V)@MAP8 [CX4002] AT24C256(1.8V)@SAP8 [CX4005]  
AT24C256(1.8V)@SOIC8 [CX1045] AT24C256(1.8V)@TSSOP8 [CX1059]  
AT24C256(2.7V) [CX0001] AT24C256(2.7V)@MAP8 [CX4002]  
AT24C256(2.7V)@SAP8 [CX4005] AT24C256(2.7V)@SOIC8 [CX1045]  
AT24C256(2.7V)@TSSOP8 [CX1059] AT24C256B [CX0001]  
AT24C256B@MAP8 [CX4002] AT24C256B@SAP8 [CX4005]  
AT24C256B@SOIC8 [CX1045] AT24C256B@TSSOP8 [CX1059]  
AT24C256C [CX0001] AT24C256C@dBGA8 [CX5156]  
AT24C256C@SOIC8 [CX1045] AT24C256C@TSSOP8 [CX1059]  
AT24C256C@UDFN8 [CX4002] AT24C32 [CX0001]  
AT24C32@SOIC8 [CX1045] AT24C32@TSSOP8 [CX1059]  
AT24C32A [CX0001] AT24C32A@MAP8 [CX4002]  
AT24C32A@SOIC8 [CX1045] AT24C32A@TSSOP8 [CX1059]  
AT24C32C [CX0001] AT24C32C@dBGA8 [CX5156]

AT24C32C@MAP8 [CX4002]  
AT24C32C@SOIC8 [CX1045]  
AT24C32D@SOIC8 [CX1045]  
AT24C32D@TSSOP8 [CX1059]  
AT24C32D@VDFN8 [CX0001]  
AT24C512(1.8V) [CX0001]  
AT24C512(1.8V)@SAP8 [CX4005]  
AT24C512(1.8V)@TSSOP8 [CX1059]  
AT24C512(2.7V)@LAP8 [CX4006]  
AT24C512(2.7V)@SOIC8 [CX1045]  
AT24C512B [CX0001]  
AT24C512B@SAP8 [CX4005]  
AT24C512B@SOIC8(150 mil) [CX1045]  
AT24C512B@SOIC8(200 mil) [CX1044]  
AT24C512B@TSSOP8 [CX1059]  
AT24C512C@SOIC8(150 mil) [CX1045]  
AT24C512C@SOIC8(200 mil) [CX1044]  
AT24C512C@TSSOP8 [CX1059]  
AT24C512C@VFBGA8 [CX5156]  
AT24C64@SOIC8 [CX1045]  
AT24C64A [CX0001]  
AT24C64A@SOIC8 [CX1045]  
AT24C64B [CX0001]  
AT24C64B@TSSOP8 [CX1059]  
AT24C64C@dBGA8 [CX5156]  
AT24C64C@SAP8 [CX4005]  
AT24C64C@TSSOP8 [CX1059]  
AT24C64D@SOT23 [CX4002]  
AT24C64D@UDFN8 [CX4002]  
AT24C64D@XBGA8 [CX0001]  
AT24CS01@SOT23 [CX1041]  
AT24CS01@UDFN8 [CX4002]  
AT24CS02@SOT23 [CX1041]  
AT24CS02@UDFN8 [CX4002]  
AT24CS04@SOT23 [CX1041]  
AT24CS04@UDFN8 [CX4002]  
AT24CS08@SOT23 [CX1041]  
AT24CS08@UDFN8 [CX4002]  
AT24CS128@SOIC8 [CX1045]  
AT24HC02B@SOIC8 [CX1045]  
AT24HC04B [CX0001]  
AT24HC04B@SOIC8 [CX1045]  
AT24MAC402@SOIC8 [CX1045]  
AT24MAC402@TSSOP8 [CX1059]  
AT24MAC602@SOIC8 [CX1045]  
AT24MAC602@TSSOP8 [CX1059]  
AT24RF08AN@SOIC8 [CX1045]  
AT24RF08BN@SOIC8 [CX1045]  
AT24RF08CN@SOIC8 [CX1045]  
AT25010 [CX0001]  
AT25010A [CX0001]  
AT25010A@TSSOP8 [CX1059]  
AT25020@SOIC8 [CX1045]  
AT25020A@SOIC8 [CX1045]  
AT25040 [CX0001]  
AT25040@SOIC8 [CX1045]  
AT25040A [CX0001]  
AT25040A@SOIC8 [CX1045]  
AT25080 [CX0001]  
AT24C32C@SAP8 [CX4005]  
AT24C32C@TSSOP8 [CX1059]  
AT24C32D@SOT23 [CX4002]  
AT24C32D@UDFN8 [CX4002]  
AT24C32D@XBGA8 [CX0001]  
AT24C512(1.8V)@LAP8 [CX4006]  
AT24C512(1.8V)@SOIC8 [CX1045]  
AT24C512(2.7V) [CX0001]  
AT24C512(2.7V)@SAP8 [CX4005]  
AT24C512(2.7V)@TSSOP8 [CX1059]  
AT24C512B@LAP8 [CX4006]  
AT24C512C@UDFN8 [CX4002]  
AT24C64 [CX0001]  
AT24C64@TSSOP8 [CX1059]  
AT24C64A@MAP8 [CX4002]  
AT24C64A@TSSOP8 [CX1059]  
AT24C64B@SOIC8 [CX1045]  
AT24C64C [CX0001]  
AT24C64C@MAP8 [CX4002]  
AT24C64C@SOIC8 [CX1045]  
AT24C64D@SOIC8 [CX1045]  
AT24C64D@TSSOP8 [CX1059]  
AT24C64D@VDFN8 [CX0001]  
AT24CS01@SOIC8 [CX1045]  
AT24CS01@TSSOP8 [CX1059]  
AT24CS02@SOIC8 [CX1045]  
AT24CS02@TSSOP8 [CX1059]  
AT24CS04@SOIC8 [CX1045]  
AT24CS04@TSSOP8 [CX1059]  
AT24CS08@SOIC8 [CX1045]  
AT24CS08@TSSOP8 [CX1059]  
AT24CS128 [CX0001]  
AT24HC02B [CX0001]  
AT24HC02B@TSSOP8 [CX1059]  
AT24HC04B@MAP8 [CX4002]  
AT24HC04B@TSSOP8 [CX1059]  
AT24MAC402@SOT23 [CX1041]  
AT24MAC402@UDFN8 [CX4002]  
AT24MAC602@SOT23 [CX1041]  
AT24MAC602@UDFN8 [CX4002]  
AT24RF08AT@TSSOP14 [CX1000]  
AT24RF08BT@TSSOP14 [CX1000]  
AT24RF08CT@TSSOP14 [CX1000]  
AT25010@SOIC8 [CX1045]  
AT25010A@SOIC8 [CX1045]  
AT25020 [CX0001]  
AT25020A [CX0001]  
AT25020A@TSSOP8 [CX1059]  
AT25040(ISP) [CX0001]  
AT25040@SOIC8(ISP)  
AT25040A(ISP) [CX0001]  
AT25040A@SOIC8(ISP)  
AT25080@SOIC8 [CX1045]

AT25080@TSSOP14 [CX1000] AT25080@TSSOP20 [CX1000]  
AT25080@TSSOP8 [CX1059] AT25080A [CX0001]  
AT25080A@SOIC8 [CX1045] AT25080A@TSSOP14 [CX1000]  
AT25080A@TSSOP8 [CX1059] AT25080B [CX0001]  
AT25080B@dBGA8 AT25080B@MAP8 [CX4002]  
AT25080B@SOIC8 [CX1045] AT25080B@TSSOP8 [CX1059]  
AT25128 [CX0001] AT25128@SOIC16 [CX1016]  
AT25128@SOIC8 [CX1045] AT25128@TSSOP14 [CX1000]  
AT25128@TSSOP20 [CX1000] AT25128A [CX0001]  
AT25128A@dBGA8 AT25128A@SAP8 [CX4005]  
AT25128A@SOIC8(4.0) [CX1045] AT25128A@SOIC8(5.4) [CX1044]  
AT25128A@TSSOP14 [CX1000] AT25128A@TSSOP8 [CX1059]  
AT25128B [CX0001] AT25128B@SOIC8 [CX1045]  
AT25128B@TSSOP8 [CX1059] AT25128B@UDFN8 [CX4002]  
AT25128B@VFBGA8 [CX0001] AT25160 [CX0001]  
AT25160@SOIC8 [CX1045] AT25160@TSSOP14 [CX1000]  
AT25160@TSSOP20 [CX1000] AT25160@TSSOP8 [CX1059]  
AT25160A [CX0001] AT25160A@SOIC8 [CX1045]  
AT25160A@TSSOP14 [CX1000] AT25160A@TSSOP8 [CX1059]  
AT25160B [CX0001] AT25160B@dBGA8  
AT25160B@MAP8 [CX4002] AT25160B@SOIC8 [CX1045]  
AT25160B@TSSOP8 [CX1059] AT25256 [CX0001]  
AT25256@SOIC16 [CX1016] AT25256@SOIC8 [CX1045]  
AT25256@TSSOP14 [CX1000] AT25256@TSSOP20 [CX1001]  
AT25256A [CX0001] AT25256A@dBGA8  
AT25256A@SAP8 [CX4005] AT25256A@SOIC8(4.0) [CX1045]  
AT25256A@SOIC8(5.4) [CX1044] AT25256A@TSSOP14 [CX1000]  
AT25256A@TSSOP8 [CX1059] AT25256B [CX0001]  
AT25256B@SOIC8 [CX1045] AT25256B@TSSOP8 [CX1059]  
AT25256B@UDFN8 [CX4002] AT25256B@VFBGA8 [CX0001]  
AT25320 [CX0001] AT25320@SOIC8 [CX1045]  
AT25320@TSSOP14 [CX1000] AT25320@TSSOP20 [CX1000]  
AT25320@TSSOP8 [CX1059] AT25320A [CX0001]  
AT25320A@SOIC8 [CX1045] AT25320A@TSSOP14 [CX1000]  
AT25320A@TSSOP8 [CX1059] AT25320B [CX0001]  
AT25320B@dBGA8 AT25320B@MAP8 [CX4002]  
AT25320B@SOIC8 [CX1045] AT25320B@TSSOP8 [CX1059]  
AT25512@SAP8 [CX4005] AT25512@SOIC8 [CX1045]  
AT25512@TSSOP8 [CX1059] AT25640 [CX0001]  
AT25640@SOIC8 [CX1045] AT25640@TSSOP14 [CX1000]  
AT25640@TSSOP20 [CX1000] AT25640@TSSOP8 [CX1059]  
AT25640A [CX0001] AT25640A@SOIC8 [CX1045]  
AT25640A@TSSOP14 [CX1000] AT25640A@TSSOP8 [CX1059]  
AT25640B [CX0001] AT25640B@dBGA8  
AT25640B@MAP8 [CX4002] AT25640B@SOIC8 [CX1045]  
AT25640B@TSSOP8 [CX1059] AT25DF021(OTP)@SOIC8 [CX1045#2]  
AT25DF021(OTP)@UDFN8 [CX4005#3] AT25DF021@SOIC8 [CX1045#2]  
AT25DF021@UDFN8 [CX4005#3] AT25DF041A@MLF8 [CX4005#3]  
AT25DF041A@SOIC8(4.0) [CX1045#2] AT25DF041A@SOIC8(5.4) [CX1044#2]  
AT25DF081@SOIC8 [CX1045#2] AT25DF081@UDFN8 [CX4005#3]  
AT25DF081A@SOIC8 [CX1044#1] AT25DF081A@UDFN8 [CX4005#3]  
AT25DF161(OTP)@SOIC8(4.0) [CX1045#2] AT25DF161@MLF8 [CX4005#3]  
AT25DF161(OTP)@SOIC8(5.4) [CX1031#2] AT25DF161@SOIC8(5.4) [CX1031#2]  
AT25DF161(OTP)@UDFN8 [CX4005#3] AT25DF321@SOIC8 [CX1031#2]  
AT25DF161@SOIC8(4.0) [CX1045#2] AT25DF321A(OTP)@SOIC16 [CX1033#2]  
AT25DF321@SOIC16 [CX1033#2] AT25DF321A(OTP)@SOIC8 [CX1031#2]  
AT25DF321A(OTP)@SOIC16 [CX1033#2] AT25DF321A(OTP)@UDFN8 [CX4005#3]  
AT25DF641(OTP)@SOIC16 [CX1033#2] AT25DF641(OTP)@VDFN8 [CX4006#3]

AT25DL161@dBGA8 [CX5156]  
AT25DL161@UDFN8 [CX4005#3]  
AT25DQ321@SOIC8 [CX1031#2]  
AT25F1024 [CX0001]  
AT25F1024(W)VQFPN8 [CX4006]  
AT25F1024@VQFPN8 [CX4005]  
AT25F1024A(W)@SOIC8 [CX1044]  
AT25F1024A@SOIC8 [CX1045]  
AT25F2048 [CX0001]  
AT25F2048(W)VQFPN8 [CX4006]  
AT25F2048@VQFPN8 [CX4005]  
AT25F2048A(W)@SOIC8 [CX1044]  
AT25F2048A@SOIC8 [CX1045]  
AT25F4096 [CX0001]  
AT25F4096(W)VQFPN8 [CX4006]  
AT25F4096@VQFPN8 [CX4005]  
AT25F4096A(W)@SOIC8 [CX1044]  
AT25F4096A@SOIC8 [CX1045]  
AT25F512 [CX0001]  
AT25F512(W)VQFPN8 [CX4006]  
AT25F512@VQFPN8 [CX4005]  
AT25F512A(W)@SOIC8 [CX1044]  
AT25F512A@SOIC8 [CX1045]  
AT25F512B@SOIC8 [CX1045]  
AT25FS010@SAP8 [CX4005]  
AT25FS040@SAP8 [CX4005]  
AT25HP256 [CX0001]  
AT25HP256@SOIC16 [CX1033]  
AT25HP256@VQFPN8 [CX4005]  
AT25HP512(W)VQFPN8 [CX4006]  
AT25HP512@SOIC8 [CX1045]  
AT25P1024@SOIC20 [CX1033]  
AT26DF041@MLF8 [CX4005]  
AT26DF041@SOIC8(5.4) [CX1044]  
AT26DF081@SOIC8(5.4) [CX1031#2]  
AT26DF081A@SOIC8(5.4) [CX1031#2]  
AT26DF161@SOIC8 [CX1031#2]  
AT26DF161A@SOIC8(4.0) [CX1045#2]  
AT26DF321@MLF8(5\*6mm) [CX4005#3]  
AT26DF321@SOIC16 [CX1033#2]  
AT26F004@MLF8 [CX4005#3]  
AT26F004@SOIC8(5.4) [CX1031#2]  
AT27011@PLCC32 [CX2032]  
AT2732A [CX0001]  
AT27BV010@PLCC32 [CX2032]  
AT27BV010@VSOP32 [CX1003]  
AT27BV020@PLCC32 [CX2032]  
AT27BV020@VSOP32 [CX1003]  
AT27BV040@PLCC32 [CX2032]  
AT27BV040@VSOP32 [CX1003]  
AT27BV1024@VSOP40 [CX1005]  
AT27BV256@PLCC32 [CX2032]  
AT27BV400@PLCC44 [CX2044]  
AT27BV400@TSOP48 [CX1004]  
AT27BV4096@PLCC44 [CX2044]  
AT27BV512 [CX0001]  
AT27BV512@SOIC28 [CX1033]  
AT27BV520@SOIC20 [CX1033]  
AT27BV520@TSSOP20 [CX1000]

AT25DL161@SOIC8 [CX1045#2]  
AT25DQ321@SOIC16 [CX1033#2]  
AT25DQ321@UDFN8 [CX4005#3]  
AT25F1024(W)@SOIC8 [CX1044]  
AT25F1024@SOIC8 [CX1045]  
AT25F1024A [CX0001]  
AT25F1024A(W)VQFPN8 [CX4006]  
AT25F1024A@VQFPN8 [CX4005]  
AT25F2048(W)@SOIC8 [CX1044]  
AT25F2048@SOIC8 [CX1045]  
AT25F2048A [CX0001]  
AT25F2048A(W)VQFPN8 [CX4006]  
AT25F2048A@VQFPN8 [CX4005]  
AT25F4096(W)@SOIC8 [CX1044]  
AT25F4096@SOIC8 [CX1045]  
AT25F4096A [CX0001]  
AT25F4096A(W)VQFPN8 [CX4006]  
AT25F4096A@VQFPN8 [CX4005]  
AT25F512(W)@SOIC8 [CX1044]  
AT25F512@SOIC8 [CX1045]  
AT25F512A [CX0001]  
AT25F512A(W)VQFPN8 [CX4006]  
AT25F512A@VQFPN8 [CX4005]  
AT25F512B@UDFN8 [CX4002]  
AT25FS010@SOIC8 [CX1045]  
AT25FS040@SOIC8 [CX1045]  
AT25HP256(W)VQFPN8 [CX4006]  
AT25HP256@SOIC8 [CX1045]  
AT25HP512 [CX0001]  
AT25HP512@SOIC16 [CX1033]  
AT25HP512@VQFPN8 [CX4005]  
AT25P1024@VQFPN8 [CX4006]  
AT26DF041@SOIC8(4.0) [CX1045]  
AT26DF081@SOIC8(4.0) [CX1045#2]  
AT26DF081A@SOIC8(4.0) [CX1045#2]  
AT26DF161@MLF8 [CX4005#3]  
AT26DF161A@MLF8 [CX4005#3]  
AT26DF161A@SOIC8(5.4) [CX1031#2]  
AT26DF321@MLF8(6\*8mm) [CX4006#2]  
AT26DF321@SOIC8 [CX1031#2]  
AT26F004@SOIC8(4.0) [CX1045#2]  
AT27011 [CX0001]  
AT27256 [CX0001]  
AT27BV010 [CX0001]  
AT27BV010@TSOP32 [CX1002]  
AT27BV020 [CX0001]  
AT27BV020@TSOP32 [CX1002]  
AT27BV040 [CX0001]  
AT27BV040@TSOP32 [CX1002]  
AT27BV1024@PLCC44 [CX2044]  
AT27BV256 [CX0001]  
AT27BV256@TSOP28 [CX1024]  
AT27BV400@PSOP44 [CX1014]  
AT27BV4096 [CX0001]  
AT27BV4096@VSOP40 [CX1005]  
AT27BV512@PLCC32 [CX2032]  
AT27BV512@TSOP28 [CX1024]  
AT27BV520@TSOP28 [CX1024]  
AT27C010 [CX0001]

AT27C010@PLCC32 [CX2032]  
AT27C010L [CX0001]  
AT27C010L@TSOP32 [CX1002]  
AT27C020@PLCC32 [CX2032]  
AT27C040 [CX0001]  
AT27C040@TSOP32 [CX1002]  
AT27C080@PLCC32 [CX2032]  
AT27C1024 [CX0001]  
AT27C1024@VSOP40 [CX1005]  
AT27C1024L@PLCC44 [CX2044]  
AT27C128@PLCC32 [CX2032]  
AT27C2048@PLCC44 [CX2044]  
AT27C256 [CX0001]  
AT27C256R [CX0001]  
AT27C256R@SOIC28 [CX1035]  
AT27C4096 [CX0001]  
AT27C4096@VSOP40 [CX1005]  
AT27C512@PLCC32 [CX2032]  
AT27C512R@PLCC32 [CX2032]  
AT27C512R@TSOP28 [CX1024]  
AT27C513@PLCC32 [CX2032]  
AT27C513R@PLCC32 [CX2032]  
AT27C515 [CX0001]  
AT27C516 [CX0001]  
AT27C516@VSOP40 [CX1005]  
AT27C520@TSOP28 [CX1024]  
AT27C64 [CX0001]  
AT27C800@PLCC44 [CX2044]  
AT27C800@TSOP48 [CX1004]  
AT27HC1024@PLCC44 [CX2044]  
AT27HC256@PLCC32 [CX2032]  
AT27HC256L@PLCC32 [CX2032]  
AT27HC256R@PLCC32 [CX2032]  
AT27HC256RL@PLCC32 [CX2032]  
AT27HC64@PLCC32 [CX2032]  
AT27HC641@PLCC28 [CX2028]  
AT27HC641R@PLCC28 [CX2028]  
AT27HC642@PLCC28 [CX2028]  
AT27HC642R@PLCC28 [CX2028]  
AT27HC64L@PLCC32 [CX2032]  
AT27LV010@PLCC32 [CX2032]  
AT27LV010@VSOP32 [CX1003]  
AT27LV010A@PLCC32 [CX2032]  
AT27LV010A@VSOP32 [CX1003]  
AT27LV020A@PLCC32 [CX2032]  
AT27LV020A@VSOP32 [CX1003]  
AT27LV040@PLCC32 [CX2032]  
AT27LV040@VSOP32 [CX1003]  
AT27LV040A@PLCC32 [CX2032]  
AT27LV040A@VSOP32 [CX1003]  
AT27LV1024@PLCC44 [CX2044]  
AT27LV1026@TSOP40 [CX1005]  
AT27LV256A@PLCC32 [CX2032]  
AT27LV256A@TSOP28 [CX1024]  
AT27LV256R@PLCC32 [CX2032]  
AT27LV256R@TSOP28 [CX1024]  
AT27LV4096@PLCC44 [CX2044]  
AT27LV512A@PLCC32 [CX2032]  
AT27LV512A@TSOP28 [CX1024]

AT27C010@TSOP32 [CX1002]  
AT27C010L@PLCC32 [CX2032]  
AT27C020 [CX0001]  
AT27C020@TSOP32 [CX1002]  
AT27C040@PLCC32 [CX2032]  
AT27C080 [CX0001]  
AT27C080@TSOP32 [CX1002]  
AT27C1024@PLCC44 [CX2044]  
AT27C1024L [CX0001]  
AT27C128 [CX0001]  
AT27C2048 [CX0001]  
AT27C2048@VSOP40 [CX1005]  
AT27C256@PLCC32 [CX2032]  
AT27C256R@PLCC32 [CX2032]  
AT27C256R@TSOP28 [CX1024]  
AT27C4096@PLCC44 [CX2044]  
AT27C512 [CX0001]  
AT27C512R [CX0001]  
AT27C512R@SOIC28 [CX1033]  
AT27C513 [CX0001]  
AT27C513@SOIC28 [CX1033]  
AT27C513R@SOIC28 [CX1033]  
AT27C515@PLCC32 [CX2032]  
AT27C516@PLCC44 [CX2044]  
AT27C520@SOIC20 [CX1033]  
AT27C520@TSSOP20 [CX1000]  
AT27C800 [CX0001]  
AT27C800@PSOP44 [CX1014]  
AT27HC1024 [CX0001]  
AT27HC256 [CX0001]  
AT27HC256L [CX0001]  
AT27HC256R [CX0001]  
AT27HC256RL [CX0001]  
AT27HC64 [CX0001]  
AT27HC641 [CX0001]  
AT27HC641R [CX0001]  
AT27HC642 [CX0001]  
AT27HC642R [CX0001]  
AT27HC64L [CX0001]  
AT27LV010 [CX0001]  
AT27LV010@TSOP32 [CX1002]  
AT27LV010A [CX0001]  
AT27LV010A@TSOP32 [CX1002]  
AT27LV020A [CX0001]  
AT27LV020A@TSOP32 [CX1002]  
AT27LV040 [CX0001]  
AT27LV040@TSOP32 [CX1002]  
AT27LV040A [CX0001]  
AT27LV040A@TSOP32 [CX1002]  
AT27LV1024 [CX0001]  
AT27LV1026@PLCC44 [CX2044]  
AT27LV256A [CX0001]  
AT27LV256A@SOIC28 [CX1035]  
AT27LV256R [CX0001]  
AT27LV256R@SOIC28 [CX1035]  
AT27LV4096 [CX0001]  
AT27LV512A [CX0001]  
AT27LV512A@SOIC28 [CX1033]  
AT27LV512R [CX0001]



AT27LV512R@PLCC32 [CX2032]  
AT27LV520@SOIC20 [CX1033]  
AT27LV520@TSOP20 [CX1000]  
AT27LV800@PSOP44 [CX1014]  
AT27RW1024@TSOP40 [CX1005]  
AT28BV16@PLCC32 [CX2032]  
AT28BV16@TSOP28 [CX1063]  
AT28BV256@PLCC32 [CX2032]  
AT28BV256@TSOP28 [CX1024]  
AT28BV64@PLCC32 [CX2032]  
AT28BV64@TSOP28 [CX1024]  
AT28BV64B@PLCC32 [CX2032]  
AT28BV64B@TSOP28 [CX1024]  
AT28C010@PLCC32 [CX2032]  
AT28C010@TSOP32 [CX1002]  
AT28C010E@PLCC32 [CX2032]  
AT28C010E@TSOP32 [CX1002]  
AT28C04@PLCC32 [CX2032]  
AT28C040@PLCC32 [CX2032]  
AT28C040@TSOP48 [CX1004]  
AT28C04E@PLCC32 [CX2032]  
AT28C04F@PLCC32 [CX2032]  
AT28C16@PLCC32 [CX2032]  
AT28C16@TSOP28 [CX1063]  
AT28C16E@PLCC32 [CX2032]  
AT28C16F@PLCC32 [CX2032]  
AT28C17@PLCC32 [CX2032]  
AT28C17E [CX0001]  
AT28C17F [CX0001]  
AT28C256 [CX0001]  
AT28C256@SOIC28 [CX1033]  
AT28C256E [CX0001]  
AT28C256E@SOIC28 [CX1033]  
AT28C256F [CX0001]  
AT28C64 [CX0001]  
AT28C64@SOIC28 [CX1033]  
AT28C64B [CX0001]  
AT28C64B@SOIC28 [CX1033]  
AT28C64E [CX0001]  
AT28C64E@TSOP28 [CX1024]  
AT28C64F@PLCC32 [CX2032]  
AT28C64X [CX0001]  
AT28C64X@SOIC28 [CX1033]  
AT28HC04 [CX0001]  
AT28HC16 [CX0001]  
AT28HC191 [CX0001]  
AT28HC256 [CX0001]  
AT28HC256@TSOP28 [CX1024]  
AT28HC256E@PLCC32 [CX2032]  
AT28HC256F@PLCC32 [CX2032]  
AT28HC256L@PLCC32 [CX2032]  
AT28HC256LE@PLCC32 [CX2032]  
AT28HC291@PLCC28 [CX2028]  
AT28HC291L@PLCC28 [CX2028]  
AT28HC64@PLCC32 [CX2032]  
AT28HC64B [CX0001]  
AT28HC64B@SOIC28 [CX1033]  
AT28HC64BF [CX0001]  
AT28HC64BF@SOIC28 [CX1033]  
AT27LV512R@TSOP28 [CX1024]  
AT27LV520@TSOP28 [CX1024]  
AT27LV800 [CX0001]  
AT27RW1024@PLCC44 [CX2044]  
AT28BV16 [CX0001]  
AT28BV16@SOIC24 [CX1033]  
AT28BV256 [CX0001]  
AT28BV256@SOIC28 [CX1033]  
AT28BV64 [CX0001]  
AT28BV64@SOIC28 [CX1033]  
AT28BV64B [CX0001]  
AT28BV64B@SOIC28 [CX1033]  
AT28C010 [CX0001]  
AT28C010@PLCC44 [CX2044]  
AT28C010E [CX0001]  
AT28C010E@PLCC44 [CX2044]  
AT28C04 [CX0001]  
AT28C040 [CX0001]  
AT28C040@PLCC44 [CX2044]  
AT28C04E [CX0001]  
AT28C04F [CX0001]  
AT28C16 [CX0001]  
AT28C16@SOIC24 [CX1033]  
AT28C16E [CX0001]  
AT28C16F [CX0001]  
AT28C17 [CX0001]  
AT28C17@SOIC28 [CX1033]  
AT28C17E@PLCC32 [CX2032]  
AT28C17F@PLCC32 [CX2032]  
AT28C256@PLCC32 [CX2032]  
AT28C256@TSOP28 [CX1024]  
AT28C256E@PLCC32 [CX2032]  
AT28C256E@TSOP28 [CX1024]  
AT28C256F@PLCC32 [CX2032]  
AT28C64@PLCC32 [CX2032]  
AT28C64@TSOP28 [CX1024]  
AT28C64B@PLCC32 [CX2032]  
AT28C64B@TSOP28 [CX1024]  
AT28C64E@PLCC32 [CX2032]  
AT28C64F [CX0001]  
AT28C64F@TSOP28 [CX1024]  
AT28C64X@PLCC32 [CX2032]  
AT28C64X@TSOP28 [CX1024]  
AT28HC04@PLCC32 [CX2032]  
AT28HC16L [CX0001]  
AT28HC191L [CX0001]  
AT28HC256@PLCC32 [CX2032]  
AT28HC256E [CX0001]  
AT28HC256F [CX0001]  
AT28HC256L [CX0001]  
AT28HC256LE [CX0001]  
AT28HC291 [CX0001]  
AT28HC291L [CX0001]  
AT28HC64 [CX0001]  
AT28HC64@TSOP28 [CX1024]  
AT28HC64B@PLCC32 [CX2032]  
AT28HC64B@TSOP28 [CX1024]  
AT28HC64BF@PLCC32 [CX2032]  
AT28HC64BF@TSOP28 [CX1024]

AT28HC64L [CX0001]  
AT28HC64L@TSOP28 [CX1024]  
AT28LV010@PLCC32 [CX2032]  
AT28LV256 [CX0001]  
AT28LV256@TSOP28 [CX1024]  
AT28LV64@PLCC32 [CX2032]  
AT28LV64B@PLCC32 [CX2032]  
AT28LV64B@TSOP28 [CX1024]  
AT28MC010@PLCC32 [CX2032]  
AT28MC010@TSOP32 [CX1002]  
AT28MC020@PLCC32 [CX2032]  
AT28MC020@TSOP32 [CX1002]  
AT28MC040@PLCC32 [CX2032]  
AT28MC040@TSOP32 [CX1002]  
AT28PC64@PLCC32 [CX2032]  
AT28PC64E [CX0001]  
AT28PC64E@TSOP28 [CX1024]  
AT29BV010A@TSOP32 [CX1002]  
AT29BV020@TSOP32 [CX1002]  
AT29C010 [CX0001]  
AT29C010@TSOP32 [CX1002]  
AT29C010A@PLCC32 [CX2032]  
AT29C020 [CX0001]  
AT29C020@TSOP32 [CX1002]  
AT29C040@PLCC32 [CX2032]  
AT29C040A [CX0001]  
AT29C040A@TSOP32 [CX1002]  
AT29C1024@TSOP48 [CX1004]  
AT29C256@PLCC32 [CX2032]  
AT29C257 [CX0001]  
AT29C512 [CX0001]  
AT29C512@TSOP32 [CX1002]  
AT29LV010@PLCC32 [CX2032]  
AT29LV010A@PLCC32 [CX2032]  
AT29LV020 [CX0001]  
AT29LV020@TSOP32 [CX1002]  
AT29LV040A@PLCC32 [CX2032]  
AT29LV1024@PLCC44 [CX2044]  
AT29LV256 [CX0001]  
AT29LV256@TSOP28 [CX1024]  
AT29LV512@PLCC32 [CX2032]  
AT30TSE002@UDFN8 [CX4002]  
AT30TSE004@UDFN8 [CX4002]  
AT30TSE752@MSOP8 [CX1015]  
AT30TSE752@UDFN8 [CX4002]  
AT30TSE754@SOIC8 [CX1045]  
AT30TSE758@MSOP8 [CX1015]  
AT30TSE758@UDFN8 [CX4002]  
AT32C16@PLCC44  
AT34C02@SOIC8 [CX1045]  
AT34C02B [CX0001]  
AT34C02B@TSSOP8 [CX1059]  
AT34C02C@dBGA8 [CX5156]  
AT34C02C@SOIC8 [CX1045]  
AT45BCM021D(page256)@SOIC8 [CX1031#1]  
AT45D011@PLCC32 [CX2032]  
AT45D011@TSSOP14 [CX1000]  
AT45D021@SOIC28 [CX1035]  
AT45D041@PLCC32 [CX2032]  
AT28HC64L@PLCC32 [CX2032]  
AT28LV010 [CX0001]  
AT28LV010@TSOP32 [CX1002]  
AT28LV256@PLCC32 [CX2032]  
AT28LV64 [CX0001]  
AT28LV64B [CX0001]  
AT28LV64B@SOIC28 [CX1033]  
AT28MC010 [CX0001]  
AT28MC010@PLCC44 [CX2044]  
AT28MC020 [CX0001]  
AT28MC020@PLCC44 [CX2044]  
AT28MC040 [CX0001]  
AT28MC040@PLCC44 [CX2044]  
AT28PC64 [CX0001]  
AT28PC64@TSOP28 [CX1024]  
AT28PC64E@PLCC32 [CX2032]  
AT29BV010A@PLCC32 [CX2032]  
AT29BV020@PLCC32 [CX2032]  
AT29BV040A@TSOP32 [CX1002]  
AT29C010@PLCC32 [CX2032]  
AT29C010A [CX0001]  
AT29C010A@TSOP32 [CX1002]  
AT29C020@PLCC32 [CX2032]  
AT29C040 [CX0001]  
AT29C040@TSOP32 [CX1002]  
AT29C040A@PLCC32 [CX2032]  
AT29C1024@PLCC44 [CX2044]  
AT29C256 [CX0001]  
AT29C256@TSOP28 [CX1024]  
AT29C257@PLCC32 [CX2032]  
AT29C512@PLCC32 [CX2032]  
AT29LV010 [CX0001]  
AT29LV010@TSOP32 [CX1002]  
AT29LV010A@TSOP32 [CX1002]  
AT29LV020@PLCC32 [CX2032]  
AT29LV040A [CX0001]  
AT29LV040A@TSOP32 [CX1002]  
AT29LV1024@TSOP48 [CX1004]  
AT29LV256@PLCC32 [CX2032]  
AT29LV512 [CX0001]  
AT29LV512@TSOP32 [CX1002]  
AT30TSE002@WDFN8 [CX4002]  
AT30TSE004@WDFN8 [CX4002]  
AT30TSE752@SOIC8 [CX1045]  
AT30TSE754@MSOP8 [CX1015]  
AT30TSE754@UDFN8 [CX4002]  
AT30TSE758@SOIC8 [CX1045]  
AT32C16 [CX0001]  
AT34C02 [CX0001]  
AT34C02@TSSOP8 [CX1059]  
AT34C02B@SOIC8 [CX1045]  
AT34C02C [CX0001]  
AT34C02C@MAP8 [CX4002]  
AT34C02C@TSSOP8 [CX1059]  
AT45D011@SOIC8 [CX1031]  
AT45D021@PLCC32 [CX2032]  
AT45D021@TSOP28 [CX1024]  
AT45D041@SOIC28 [CX1035]

AT45D041@TSOP28 [CX1024] AT45D081@SOIC28 [CX1035]  
AT45D081@TSOP32 [CX1002] AT45D161@PLCC32 [CX2032]  
AT45D161@SOIC28 [CX1035] AT45D161@TSOP28 [CX1024]  
AT45DB011@PLCC32 [CX2032] AT45DB011@SOIC8 [CX1031]  
AT45DB011@TSSOP14 [CX1000] AT45DB011B@PLCC32 [CX2032]  
AT45DB011B@SOIC8 [CX1031] AT45DB011B@TSSOP14 [CX1000]  
AT45DB011D@SOIC8 [CX1031-1]  
AT45DB011D@SOIC8[150 mil] [CX1016-1]  
AT45DB011D@UDFN8 [CX4005-2] AT45DB021@PLCC32 [CX2032]  
AT45DB021@SOIC28 [CX1035] AT45DB021@TSOP28 [CX1024]  
AT45DB021A@PLCC32 [CX2032] AT45DB021A@SOIC28 [CX1035]  
AT45DB021A@TSOP28 [CX1024] AT45DB021B@CBGA9 [CX50UN]  
AT45DB021B@SOIC28 [CX1035] AT45DB021B@SOIC8 [CX1031]  
AT45DB021B@TSOP28 [CX1024] AT45DB021D@SOIC8 [CX1031-1]  
AT45DB021D@SOIC8[150 mil] [CX1016-1]  
AT45DB021D@UDFN8 [CX4005-2] AT45DB041@PLCC32 [CX2032]  
AT45DB041@SOIC28 [CX1035] AT45DB041@TSOP28 [CX1024]  
AT45DB041A@PLCC32 [CX2032] AT45DB041A@SOIC28 [CX1035]  
AT45DB041A@TSOP28 [CX1024] AT45DB041B@CASON8 [CX4006]  
AT45DB041B@CBGA14 [CX50UN] AT45DB041B@SOIC28 [CX1035]  
AT45DB041B@SOIC8 [CX1031] AT45DB041B@TSOP28 [CX1024]  
AT45DB041D(page256)@MLF8 [CX4005#2]  
AT45DB041D(page256)@SOIC8[150] [CX1016#1]  
AT45DB041D(page256)@SOIC8[200] [CX1031#1]  
AT45DB041D(page264)@MLF8 [CX4005-2]  
AT45DB041D(page264)@SOIC8[150] [CX1016-1]  
AT45DB041D(page264)@SOIC8[200] [CX1031-1]  
AT45DB041E(page256)@MLF8 [CX4005#2]  
AT45DB041E(page256)@SOIC8[150] [CX1016#1]  
AT45DB041E(page256)@SOIC8[200] [CX1031#1]  
AT45DB041E(page264)@MLF8 [CX4005-2]  
AT45DB041E(page264)@SOIC8[150] [CX1016-1]  
AT45DB041E(page264)@SOIC8[200] [CX1031-1]  
AT45DB081@SOIC28 [CX1035] AT45DB081@TSOP32 [CX1002]  
AT45DB081A@PLCC32 [CX2032] AT45DB081A@SOIC28 [CX1035]  
AT45DB081A@TSOP28 [CX1024] AT45DB081B@CASON8 [CX4006]  
AT45DB081B@CBGA14 [CX50UN] AT45DB081B@SOIC28 [CX1035]  
AT45DB081B@SOIC8 [CX1031] AT45DB081B@TSOP28 [CX1024]  
AT45DB081D(256 byte)@MLF8 [CX4005-2]  
AT45DB081D(256 byte)@SOIC8 [CX1031-1]  
AT45DB081D(256 byte)@SOIC8[150] [CX1016-1]  
AT45DB081D@MLF8 [CX4005-2] AT45DB081D@SOIC8 [CX1031-1]  
AT45DB081D@SOIC8[150 mil] [CX1016-1]  
AT45DB161@PLCC32 [CX2032] AT45DB161@SOIC28 [CX1035]  
AT45DB161@TSOP28 [CX1024] AT45DB161B@CASON8 [CX4006]  
AT45DB161B@SOIC28 [CX1035] AT45DB161B@TSOP28 [CX1024]  
AT45DB161D(page512)@SOIC8 [CX1031-1]  
AT45DB161D(page528)@SOIC8 [CX1031-1]  
AT45DB161E@QFN8[512B] [CX4005] AT45DB161E@QFN8[528B] [CX4005]  
AT45DB161E@SOIC8(150 mil)[512B] [CX1016]  
AT45DB161E@SOIC8(150 mil)[528B] [CX1016]  
AT45DB161E@SOIC8[512B] [CX1031] AT45DB161E@SOIC8[528B] [CX1031]  
AT45DB321@TSOP32 [CX1002] AT45DB321B@SOIC28 [CX1035]  
AT45DB321B@TSOP32 [CX1002] AT45DB321C@CASON8 [CX4006]  
AT45DB321C@SOIC28 [CX1035] AT45DB321C@TSOP28 [CX1024]  
AT45DB321D@QFN8[5\*6mm] [CX4005#2]  
AT45DB321D@QFN8[5\*6mm][page512] [CX4005#2]  
AT45DB321D@QFN8[6\*8mm] [CX4006#3]  
AT45DB321D@QFN8[6\*8mm][page512] [CX4006#3]

AT45DB321D@SOIC8 [CX1031#1]  
AT45DB321D@SOIC8[page512] [CX1031#1]  
AT45DB321D@TSOP28 [CX1024#1]  
AT45DB321D@TSOP28[page512] [CX1024#1]  
AT45DB642@TSOP40 [CX1006] AT45DB642D@CAS0N8 [CX4006#3]  
AT45DB642D@CAS0N8(ISP) [CX0001]  
AT45DB642D@CAS0N8[page1024] [CX4006-3]  
AT45DB642D@TSOP28 [CX1024#1] AT45DB642D@TSOP28(ISP) [CX0001]  
AT45DB642D@TSOP28[page1024] [CX1024-1]  
AT49BN1604@TSOP56 [CX1011] AT49BN1604T@TSOP56 [CX1011]  
AT49BV001 [CX0001] AT49BV001@PLCC32 [CX2032]  
AT49BV001@TSOP32 [CX1002] AT49BV001@VSOP32 [CX1003]  
AT49BV001A [CX0001] AT49BV001A@PLCC32 [CX2032]  
AT49BV001A@TSOP32 [CX1002] AT49BV001A@VSOP32 [CX1003]  
AT49BV001AN [CX0001] AT49BV001AN@PLCC32 [CX2032]  
AT49BV001AN@TSOP32 [CX1002] AT49BV001AN@VSOP32 [CX1003]  
AT49BV001ANT [CX0001] AT49BV001ANT@PLCC32 [CX2032]  
AT49BV001ANT@TSOP32 [CX1002] AT49BV001ANT@VSOP32 [CX1003]  
AT49BV001AT [CX0001] AT49BV001AT@PLCC32 [CX2032]  
AT49BV001AT@TSOP32 [CX1002] AT49BV001AT@VSOP32 [CX1003]  
AT49BV001N [CX0001] AT49BV001N@PLCC32 [CX2032]  
AT49BV001N@TSOP32 [CX1002] AT49BV001N@VSOP32 [CX1003]  
AT49BV001NT [CX0001] AT49BV001NT@PLCC32 [CX2032]  
AT49BV001NT@TSOP32 [CX1002] AT49BV001NT@VSOP32 [CX1003]  
AT49BV001T [CX0001] AT49BV001T@PLCC32 [CX2032]  
AT49BV001T@TSOP32 [CX1002] AT49BV001T@VSOP32 [CX1003]  
AT49BV002 [CX0001] AT49BV002@PLCC32 [CX2032]  
AT49BV002@TSOP32 [CX1002] AT49BV002@VSOP32 [CX1003]  
AT49BV002A [CX0001] AT49BV002A@PLCC32 [CX2032]  
AT49BV002A@TSOP32 [CX1002] AT49BV002A@VSOP32 [CX1003]  
AT49BV002AN [CX0001] AT49BV002AN@PLCC32 [CX2032]  
AT49BV002AN@TSOP32 [CX1002] AT49BV002AN@VSOP32 [CX1003]  
AT49BV002ANT [CX0001] AT49BV002ANT@PLCC32 [CX2032]  
AT49BV002ANT@TSOP32 [CX1002] AT49BV002ANT@VSOP32 [CX1003]  
AT49BV002AT [CX0001] AT49BV002AT@PLCC32 [CX2032]  
AT49BV002AT@TSOP32 [CX1002] AT49BV002AT@VSOP32 [CX1003]  
AT49BV002N [CX0001] AT49BV002N@PLCC32 [CX2032]  
AT49BV002N@TSOP32 [CX1002] AT49BV002N@VSOP32 [CX1003]  
AT49BV002NT [CX0001] AT49BV002NT@PLCC32 [CX2032]  
AT49BV002NT@TSOP32 [CX1002] AT49BV002NT@VSOP32 [CX1003]  
AT49BV002T [CX0001] AT49BV002T@PLCC32 [CX2032]  
AT49BV002T@TSOP32 [CX1002] AT49BV002T@VSOP32 [CX1003]  
AT49BV008@TSOP40 [CX1006] AT49BV008A@TSOP40 [CX1006]  
AT49BV008A@uBGA48 [CX5031] AT49BV008AT@TSOP40 [CX1006]  
AT49BV008AT@uBGA48 [CX5031] AT49BV010 [CX0001]  
AT49BV010@PLCC32 [CX2032] AT49BV010@TSOP32 [CX1002]  
AT49BV010@VSOP32 [CX1003] AT49BV020 [CX0001]  
AT49BV020@PLCC32 [CX2032] AT49BV020@TSOP32 [CX1002]  
AT49BV020@VSOP32 [CX1003] AT49BV040 [CX0001]  
AT49BV040@PLCC32 [CX2032] AT49BV040@TSOP32 [CX1002]  
AT49BV040@VSOP32 [CX1003] AT49BV040A@PLCC32 [CX2032]  
AT49BV040A@TSOP32 [CX1002] AT49BV040A@VSOP32 [CX1003]  
AT49BV040B@PLCC32 [CX2032] AT49BV040B@TSOP32 [CX1002]  
AT49BV040B@VSOP32 [CX1003] AT49BV040T [CX0001]  
AT49BV040T@PLCC32 [CX2032] AT49BV040T@TSOP32 [CX1002]  
AT49BV040T@VSOP32 [CX1003] AT49BV080@PSOP44 [CX1014]  
AT49BV080@TSOP40 [CX1006] AT49BV080T@PSOP44 [CX1014]  
AT49BV080T@TSOP40 [CX1006] AT49BV1024A@TSOP40 [CX1005]  
AT49BV160@TSOP48 [CX1004] AT49BV160@uBGA48 [CX5080]

AT49BV1604@TSOP48 [CX1004]  
AT49BV1604A@TSOP48 [CX1004]  
AT49BV1604AT@TSOP48 [CX1004]  
AT49BV1604T@TSOP48 [CX1004]  
AT49BV160C@TSOP48 [CX1004]  
AT49BV160CT@TSOP48 [CX1004]  
AT49BV160D@TSOP48 [CX1004]  
AT49BV160S@FBGA64 [CX5100]  
AT49BV160T@TSOP48 [CX1004]  
AT49BV161@CBGA48 [CX5002]  
AT49BV1614@CBGA48 [CX5005]  
AT49BV1614A@CBGA48 [CX5002]  
AT49BV1614AT@CBGA48 [CX5002]  
AT49BV1614T@CBGA48 [CX5005]  
AT49BV1618@CBGA48 [CX5005]  
AT49BV1618T@CBGA48 [CX5005]  
AT49BV161T@CBGA48 [CX5002]  
AT49BV162A@CBGA48 [CX5025]  
AT49BV162AT@CBGA48 [CX5025]  
AT49BV163A@CBGA48 [CX5002]  
AT49BV163AT@CBGA48 [CX5002]  
AT49BV163D@FBGA48 [CX5002]  
AT49BV163DT@FBGA48 [CX5002]  
AT49BV2048@PSOP44 [CX1014]  
AT49BV2048A@PSOP44 [CX1014]  
AT49BV2048B@TSOP48 [CX1004]  
AT49BV320@uBGA48 [CX50UN]  
AT49BV320A@TSOP48 [CX1004]  
AT49BV320AT@TSOP48 [CX1004]  
AT49BV320C@uBGA48 [CX5078]  
AT49BV320CT@uBGA48 [CX5078]  
AT49BV320D@TSOP48 [CX1004]  
AT49BV320DT@TSOP48 [CX1004]  
AT49BV320ST@FBGA64 [CX5100]  
AT49BV320T@uBGA48 [CX50UN]  
AT49BV321@TSOP48 [CX1004]  
AT49BV3214T@TSOP48 [CX1004]  
AT49BV3218@TSOP48 [CX1004]  
AT49BV3218T@TSOP48 [CX1004]  
AT49BV321T@TSOP48 [CX1004]  
AT49BV322A@TSOP48 [CX1004]  
AT49BV322AT@TSOP48 [CX1004]  
AT49BV322D@TSOP48 [CX1004]  
AT49BV322DT@TSOP48 [CX1004]  
AT49BV4096@TSOP48 [CX1004]  
AT49BV4096A@TSOP48 [CX1004]  
AT49BV512 [CX0001]  
AT49BV512@TSOP32 [CX1002]  
AT49BV640D@FBGA48 [CX5078]  
AT49BV640DT@FBGA48 [CX5078]  
AT49BV640S@FBGA64 [CX5100]  
AT49BV6416@TSOP48 [CX1004]  
AT49BV642D@TSOP48 [CX1004]  
AT49BV8004@CBGA48 [CX5050]  
AT49BV8004T@CBGA48 [CX5050]  
AT49BV8011@CBGA48 [CX5050]  
AT49BV8011T@CBGA48 [CX5050]  
AT49BV802A@CBGA48 [CX5002]  
AT49BV802AT@CBGA48 [CX5002]  
AT49BV1604@uBGA48 [CX5080]  
AT49BV1604A@uBGA48 [CX5080]  
AT49BV1604AT@uBGA48 [CX5080]  
AT49BV1604T@uBGA48 [CX5080]  
AT49BV160C@uBGA48 [CX50UN]  
AT49BV160CT@uBGA48 [CX50UN]  
AT49BV160DT@TSOP48 [CX1004]  
AT49BV160ST@FBGA64 [CX5100]  
AT49BV160T@uBGA48 [CX5080]  
AT49BV161@TSOP48 [CX1004]  
AT49BV1614@TSOP48 [CX1004]  
AT49BV1614A@TSOP48 [CX1004]  
AT49BV1614AT@TSOP48 [CX1004]  
AT49BV1614T@TSOP48 [CX1004]  
AT49BV1618@TSOP48 [CX1004]  
AT49BV1618T@TSOP48 [CX1004]  
AT49BV161T@TSOP48 [CX1004]  
AT49BV162A@TSOP48 [CX1004]  
AT49BV162AT@TSOP48 [CX1004]  
AT49BV163A@TSOP48 [CX1004]  
AT49BV163AT@TSOP48 [CX1004]  
AT49BV163D@TSOP48 [CX1004]  
AT49BV163DT@TSOP48 [CX1004]  
AT49BV2048@TSOP48 [CX1004]  
AT49BV2048A@TSOP48 [CX1004]  
AT49BV320@TSOP48 [CX1004]  
AT49BV320A@CBGA48 [CX5078]  
AT49BV320AT@CBGA48 [CX5078]  
AT49BV320C@TSOP48 [CX1004]  
AT49BV320CT@TSOP48 [CX1004]  
AT49BV320D@FBGA48 [CX5078]  
AT49BV320DT@FBGA48 [CX5078]  
AT49BV320S@FBGA64 [CX5100]  
AT49BV320T@TSOP48 [CX1004]  
AT49BV321@CBGA48 [CX5001]  
AT49BV3214T@CBGA48 [CX5005]  
AT49BV3218@CBGA48 [CX5005]  
AT49BV3218T@CBGA48 [CX5005]  
AT49BV321T@CBGA48 [CX5001]  
AT49BV322A@FBGA48 [CX5025]  
AT49BV322AT@FBGA48 [CX5025]  
AT49BV322D@FBGA48 [CX5025]  
AT49BV322DT@FBGA48 [CX5025]  
AT49BV4096@PSOP44 [CX1014]  
AT49BV4096A@PSOP44 [CX1014]  
AT49BV4096A@uBGA48 [CX50UN]  
AT49BV512@PLCC32 [CX2032]  
AT49BV512@VSOP32 [CX1003]  
AT49BV640D@TSOP56 [CX1011]  
AT49BV640DT@TSOP56 [CX1011]  
AT49BV640ST@FBGA64 [CX5100]  
AT49BV6416T@TSOP48 [CX1004]  
AT49BV642DT@TSOP48 [CX1004]  
AT49BV8004@TSOP48 [CX1004]  
AT49BV8004T@TSOP48 [CX1004]  
AT49BV8011@TSOP48 [CX1004]  
AT49BV8011T@TSOP48 [CX1004]  
AT49BV802A@TSOP48 [CX1004]  
AT49BV802AT@TSOP48 [CX1004]

AT49BV802D@CBGA48 [CX5002]  
AT49BV802DT@CBGA48 [CX5002]  
AT49BV8192@PSOP44 [CX1014]  
AT49BV8192A@PSOP44 [CX1014]  
AT49BV8192A@uBGA48 [CX50UN]  
AT49BV8192AT@TSOP48 [CX1004]  
AT49BV8192T@PSOP44 [CX1014]  
AT49F001 [CX0001]  
AT49F001@TSOP32 [CX1002]  
AT49F001A [CX0001]  
AT49F001A@TSOP32 [CX1002]  
AT49F001AN [CX0001]  
AT49F001AN@TSOP32 [CX1002]  
AT49F001ANT [CX0001]  
AT49F001ANT@TSOP32 [CX1002]  
AT49F001AT [CX0001]  
AT49F001AT@TSOP32 [CX1002]  
AT49F001N [CX0001]  
AT49F001N@TSOP32 [CX1002]  
AT49F001NT [CX0001]  
AT49F001NT@TSOP32 [CX1002]  
AT49F001T [CX0001]  
AT49F001T@TSOP32 [CX1002]  
AT49F002 [CX0001]  
AT49F002@TSOP32 [CX1002]  
AT49F002A [CX0001]  
AT49F002A@TSOP32 [CX1002]  
AT49F002AN [CX0001]  
AT49F002AN@TSOP32 [CX1002]  
AT49F002ANT [CX0001]  
AT49F002ANT@TSOP32 [CX1002]  
AT49F002AT [CX0001]  
AT49F002AT@TSOP32 [CX1002]  
AT49F002N [CX0001]  
AT49F002N@TSOP32 [CX1002]  
AT49F002NT [CX0001]  
AT49F002NT@TSOP32 [CX1002]  
AT49F002T [CX0001]  
AT49F002T@TSOP32 [CX1002]  
AT49F008@TSOP40 [CX1006]  
AT49F008AT@TSOP40 [CX1006]  
AT49F010@PLCC32 [CX2032]  
AT49F020 [CX0001]  
AT49F020@TSOP32 [CX1002]  
AT49F040@PLCC32 [CX2032]  
AT49F040A [CX0001]  
AT49F040A@TSOP32 [CX1002]  
AT49F040T@PLCC32 [CX2032]  
AT49F080@PSOP44 [CX1014]  
AT49F080T@PSOP44 [CX1014]  
AT49F1024@TSOP40 [CX1005]  
AT49F1025@PLCC44 [CX2044]  
AT49F1604@TSOP48 [CX1004]  
AT49F1604T@TSOP48 [CX1004]  
AT49F1614@CBGA48 [CX5005]  
AT49F1614T@CBGA48 [CX5005]  
AT49F2048@PSOP44 [CX1014]  
AT49F2048A@PSOP44 [CX1014]  
AT49F4096@PSOP44 [CX1014]

AT49BV802D@TSOP48 [CX1004]  
AT49BV802DT@TSOP48 [CX1004]  
AT49BV8192@TSOP48 [CX1004]  
AT49BV8192A@TSOP48 [CX1004]  
AT49BV8192AT@PSOP44 [CX1014]  
AT49BV8192AT@uBGA48 [CX50UN]  
AT49BV8192T@TSOP48 [CX1004]  
AT49F001@PLCC32 [CX2032]  
AT49F001@VSOP32 [CX1003]  
AT49F001A@PLCC32 [CX2032]  
AT49F001A@VSOP32 [CX1003]  
AT49F001AN@PLCC32 [CX2032]  
AT49F001AN@VSOP32 [CX1003]  
AT49F001ANT@PLCC32 [CX2032]  
AT49F001ANT@VSOP32 [CX1003]  
AT49F001AT@PLCC32 [CX2032]  
AT49F001AT@VSOP32 [CX1003]  
AT49F001N@PLCC32 [CX2032]  
AT49F001N@VSOP32 [CX1003]  
AT49F001NT@PLCC32 [CX2032]  
AT49F001NT@VSOP32 [CX1003]  
AT49F001T@PLCC32 [CX2032]  
AT49F001T@VSOP32 [CX1003]  
AT49F002@PLCC32 [CX2032]  
AT49F002@VSOP32 [CX1003]  
AT49F002A@PLCC32 [CX2032]  
AT49F002A@VSOP32 [CX1003]  
AT49F002AN@PLCC32 [CX2032]  
AT49F002AN@VSOP32 [CX1003]  
AT49F002ANT@PLCC32 [CX2032]  
AT49F002ANT@VSOP32 [CX1003]  
AT49F002AT@PLCC32 [CX2032]  
AT49F002AT@VSOP32 [CX1003]  
AT49F002N@PLCC32 [CX2032]  
AT49F002N@VSOP32 [CX1003]  
AT49F002NT@PLCC32 [CX2032]  
AT49F002NT@VSOP32 [CX1003]  
AT49F002T@PLCC32 [CX2032]  
AT49F002T@VSOP32 [CX1003]  
AT49F008A@TSOP40 [CX1006]  
AT49F010 [CX0001]  
AT49F010@TSOP32 [CX1002]  
AT49F020@PLCC32 [CX2032]  
AT49F040 [CX0001]  
AT49F040@TSOP32 [CX1002]  
AT49F040A@PLCC32 [CX2032]  
AT49F040T [CX0001]  
AT49F040T@TSOP32 [CX1002]  
AT49F080@TSOP40 [CX1006]  
AT49F080T@TSOP40 [CX1006]  
AT49F1024A@TSOP40 [CX1005]  
AT49F1025@TSOP40 [CX1005]  
AT49F1604@uBGA48 [CX50UN]  
AT49F1604T@uBGA48 [CX50UN]  
AT49F1614@TSOP48 [CX1004]  
AT49F1614T@TSOP48 [CX1004]  
AT49F2048@TSOP48 [CX1004]  
AT49F2048A@TSOP48 [CX1004]  
AT49F4096@TSOP48 [CX1004]

AT49F4096A@CBGA48 [CX5002]  
AT49F4096A@TSOP48 [CX1004]  
AT49F512 [CX0001]  
AT49F512@TSOP32 [CX1002]  
AT49F516@PLCC44 [CX2044]  
AT49F8004@CBGA48 [CX5050]  
AT49F8004T@CBGA48 [CX5050]  
AT49F8011@CBGA48 [CX5050]  
AT49F8011T@CBGA48 [CX5050]  
AT49F8192@PSOP44 [CX1014]  
AT49F8192A@PSOP44 [CX1014]  
AT49F8192AT@PSOP44 [CX1014]  
AT49F8192T@PSOP44 [CX1014]  
AT49HBV010 [CX0001]  
AT49HBV010@TSOP32 [CX1002]  
AT49HF010 [CX0001]  
AT49HF010@TSOP32 [CX1002]  
AT49HLV010@PLCC32 [CX2032]  
AT49HLV010@VSOP32 [CX1003]  
AT49LH002@TSOP40 [CX1006]  
AT49LH004@TSOP40 [CX1006]  
AT49LH00B4@TSOP40 [CX1006]  
AT49LL020@TSOP40 [CX1006]  
AT49LL040@TSOP40 [CX1006]  
AT49LL080@TSOP40 [CX1006]  
AT49LV001@PLCC32 [CX2032]  
AT49LV001@VSOP32 [CX1003]  
AT49LV001N@PLCC32 [CX2032]  
AT49LV001N@VSOP32 [CX1003]  
AT49LV001NT@PLCC32 [CX2032]  
AT49LV001NT@VSOP32 [CX1003]  
AT49LV001T@PLCC32 [CX2032]  
AT49LV001T@VSOP32 [CX1003]  
AT49LV002@PLCC32 [CX2032]  
AT49LV002@VSOP32 [CX1003]  
AT49LV002N@PLCC32 [CX2032]  
AT49LV002N@VSOP32 [CX1003]  
AT49LV002NT@PLCC32 [CX2032]  
AT49LV002NT@VSOP32 [CX1003]  
AT49LV002T@PLCC32 [CX2032]  
AT49LV002T@VSOP32 [CX1003]  
AT49LV008A@TSOP40 [CX1006]  
AT49LV008AT@TSOP40 [CX1006]  
AT49LV010 [CX0001]  
AT49LV010@TSOP32 [CX1002]  
AT49LV020 [CX0001]  
AT49LV020@TSOP32 [CX1002]  
AT49LV040 [CX0001]  
AT49LV040@TSOP32 [CX1002]  
AT49LV040T [CX0001]  
AT49LV040T@TSOP32 [CX1002]  
AT49LV080@PSOP44 [CX1014]  
AT49LV080T@PSOP44 [CX1014]  
AT49LV1024@TSOP40 [CX1005]  
AT49LV1025@PLCC44 [CX2044]  
AT49LV1604@TSOP48 [CX1004]  
AT49LV1604T@TSOP48 [CX1004]  
AT49LV160T@TSOP48 [CX1004]  
AT49LV161@TSOP48 [CX1004]  
AT49F4096A@PSOP44 [CX1014]  
AT49F4096A@uBGA48 [CX50UN]  
AT49F512@PLCC32 [CX2032]  
AT49F512@VSOP32 [CX1003]  
AT49F516@TSOP40 [CX1005]  
AT49F8004@TSOP48 [CX1004]  
AT49F8004T@TSOP48 [CX1004]  
AT49F8011@TSOP48 [CX1004]  
AT49F8011T@TSOP48 [CX1004]  
AT49F8192@TSOP48 [CX1004]  
AT49F8192A@TSOP48 [CX1004]  
AT49F8192AT@TSOP48 [CX1004]  
AT49F8192T@TSOP48 [CX1004]  
AT49HBV010@PLCC32 [CX2032]  
AT49HBV010@VSOP32 [CX1003]  
AT49HF010@PLCC32 [CX2032]  
AT49HLV010 [CX0001]  
AT49HLV010@TSOP32 [CX1002]  
AT49LH002@PLCC32 [CX2032]  
AT49LH004@PLCC32 [CX2032]  
AT49LH00B4@PLCC32 [CX2032]  
AT49LL020@PLCC32 [CX2032]  
AT49LL040@PLCC32 [CX2032]  
AT49LL080@PLCC32 [CX2032]  
AT49LV001 [CX0001]  
AT49LV001@TSOP32 [CX1002]  
AT49LV001N [CX0001]  
AT49LV001N@TSOP32 [CX1002]  
AT49LV001NT [CX0001]  
AT49LV001NT@TSOP32 [CX1002]  
AT49LV001T [CX0001]  
AT49LV001T@TSOP32 [CX1002]  
AT49LV002 [CX0001]  
AT49LV002@TSOP32 [CX1002]  
AT49LV002N [CX0001]  
AT49LV002N@TSOP32 [CX1002]  
AT49LV002NT [CX0001]  
AT49LV002NT@TSOP32 [CX1002]  
AT49LV002T [CX0001]  
AT49LV002T@TSOP32 [CX1002]  
AT49LV008@TSOP40 [CX1006]  
AT49LV008A@uBGA48 [CX5031]  
AT49LV008AT@uBGA48 [CX5031]  
AT49LV010@PLCC32 [CX2032]  
AT49LV010@VSOP32 [CX1003]  
AT49LV020@PLCC32 [CX2032]  
AT49LV020@VSOP32 [CX1003]  
AT49LV040@PLCC32 [CX2032]  
AT49LV040@VSOP32 [CX1003]  
AT49LV040T@PLCC32 [CX2032]  
AT49LV040T@VSOP32 [CX1003]  
AT49LV080@TSOP40 [CX1006]  
AT49LV080T@TSOP40 [CX1006]  
AT49LV1024A@TSOP40 [CX1005]  
AT49LV160@TSOP48 [CX1004]  
AT49LV1604@uBGA48 [CX5080]  
AT49LV1604T@uBGA48 [CX5080]  
AT49LV161@CBGA48 [CX5002]  
AT49LV1614@CBGA48 [CX5005]

AT49LV1614@TSOP48 [CX1004]  
AT49LV1614A@TSOP48 [CX1004]  
AT49LV1614AT@TSOP48 [CX1004]  
AT49LV1614T@TSOP48 [CX1004]  
AT49LV161T@TSOP48 [CX1004]  
AT49LV2048@TSOP48 [CX1004]  
AT49LV2048A@TSOP48 [CX1004]  
AT49LV320@TSOP48 [CX1004]  
AT49LV320T@TSOP48 [CX1004]  
AT49LV321@CBGA48 [CX5001]  
AT49LV3218@CBGA48 [CX5005]  
AT49LV3218T@CBGA48 [CX5005]  
AT49LV321T@CBGA48 [CX5001]  
AT49LV4096A@CBGA48 [CX5002]  
AT49LV4096A@TSOP48 [CX1004]  
AT49LV8011@CBGA48 [CX5050]  
AT49LV8011T@CBGA48 [CX5050]  
AT49LV8192@PSOP44 [CX1014]  
AT49LV8192A@PSOP44 [CX1014]  
AT49LV8192A@uBGA48 [CX50UN]  
AT49LV8192AT@TSOP48 [CX1004]  
AT49LV8192T@PSOP44 [CX1014]  
AT49LW040@PLCC32 [CX2032]  
AT49LW080@PLCC32 [CX2032]  
AT49SV163D@CBGA48 [CX5025]  
AT49SV163DT@CBGA48 [CX5025]  
AT49SV322A@CBGA48 [CX5025]  
AT49SV322AT@CBGA48 [CX5025]  
AT49SV322D@FBGA48 [CX5025]  
AT49SV322DT@FBGA48 [CX5025]  
AT49SV802A@CBGA48 [CX5002]  
AT49SV802AT@CBGA48 [CX5002]  
AT52BC1660A@FBGA66 [CX5005]  
AT52BC1661A@FBGA66 [CX5005]  
AT52BC1661D@FBGA66 [CX5005]  
AT52BC3221A@FBGA66 [CX5005]  
AT52BC3221D@FBGA66 [CX5005]  
AT52BC6402A@FBGA66 [CX5001]  
AT52BR1662@CBGA66 [CX5005]  
AT52BR1662AT@CBGA66 [CX5005]  
AT52BR1664@CBGA66 [CX5005]  
AT52BR1664AT@CBGA66 [CX5005]  
AT52BR1672@CBGA66 [CX5005]  
AT52BR1674@CBGA66 [CX5005]  
AT52BR3218A@CBGA66 [CX5005]  
AT52BR3224A@CBGA66 [CX5005]  
AT52BR3228A@CBGA66 [CX5005]  
AT52BR3244@CBGA66 [CX5001]  
AT52BR3248@CBGA66 [CX5001]  
AT52BR6408A@CSP66 [CX5001]  
AT59C11 [CX0001]  
AT59C12 [CX0001]  
AT59C13 [CX0001]  
AT59C22 [CX0001]  
AT88SC0104 [CX0001-1]  
AT88SC0204 [CX0001-1]  
AT88SC0404@SOIC8 [CX1016-2]  
AT93C46(08bit) [CX0001]  
AT93C46(08bit)@TSSOP8 [CX1059]

AT49LV1614A@CBGA48 [CX5002]  
AT49LV1614AT@CBGA48 [CX5002]  
AT49LV1614T@CBGA48 [CX5005]  
AT49LV161T@CBGA48 [CX5002]  
AT49LV2048@PSOP44 [CX1014]  
AT49LV2048A@PSOP44 [CX1014]  
AT49LV2048B@TSOP48 [CX1004]  
AT49LV320@uBGA48 [CX50UN]  
AT49LV320T@uBGA48 [CX50UN]  
AT49LV321@TSOP48 [CX1004]  
AT49LV3218@TSOP48 [CX1004]  
AT49LV3218T@TSOP48 [CX1004]  
AT49LV321T@TSOP48 [CX1004]  
AT49LV4096A@PSOP44 [CX1014]  
AT49LV4096A@uBGA48 [CX50UN]  
AT49LV8011@TSOP48 [CX1004]  
AT49LV8011T@TSOP48 [CX1004]  
AT49LV8192@TSOP48 [CX1004]  
AT49LV8192A@TSOP48 [CX1004]  
AT49LV8192AT@PSOP44 [CX1014]  
AT49LV8192AT@uBGA48 [CX50UN]  
AT49LV8192T@TSOP48 [CX1004]  
AT49LW040@TSOP40 [CX1006]  
AT49LW080@TSOP40 [CX1006]  
AT49SV163D@TSOP48 [CX1004]  
AT49SV163DT@TSOP48 [CX1004]  
AT49SV322A@TSOP48 [CX1004]  
AT49SV322AT@TSOP48 [CX1004]  
AT49SV322D@TSOP48 [CX1004]  
AT49SV322DT@TSOP48 [CX1004]  
AT49SV802A@TSOP48 [CX1004]  
AT49SV802AT@TSOP48 [CX1004]  
AT52BC1660AT@FBGA66 [CX5005]  
AT52BC1661AT@FBGA66 [CX5005]  
AT52BC1661DT@FBGA66 [CX5005]  
AT52BC3221AT@FBGA66 [CX5005]  
AT52BC3221DT@FBGA66 [CX5005]  
AT52BC6402AT@FBGA66 [CX5001]  
AT52BR1662A@CBGA66 [CX5005]  
AT52BR1662T@CBGA66 [CX5005]  
AT52BR1664A@CBGA66 [CX5005]  
AT52BR1664T@CBGA66 [CX5005]  
AT52BR1672T@CBGA66 [CX5005]  
AT52BR1674T@CBGA66 [CX5005]  
AT52BR3218AT@CBGA66 [CX5005]  
AT52BR3224AT@CBGA66 [CX5005]  
AT52BR3228AT@CBGA66 [CX5005]  
AT52BR3244T@CBGA66 [CX5001]  
AT52BR3248T@CBGA66 [CX5001]  
AT52BR6408AT@CSP66 [CX5001]  
AT59C11@SOIC8 [CX1045]  
AT59C12@SOIC8 [CX1045]  
AT59C13@SOIC8 [CX1045]  
AT59C22@SOIC8 [CX1045]  
AT88SC0104@SOIC8 [CX1016-2]  
AT88SC0204@SOIC8 [CX1016-2]  
AT88SC0808@SOIC8 [CX1016-2]  
AT93C46(08bit)@SOIC8 [CX1045]  
AT93C46(16bit) [CX0001]



AT93C46(16bit)@SOIC8 [CX1045]	AT93C46(16bit)@TSSOP8 [CX1059]
AT93C46A [CX0001]	AT93C46A@SOIC8 [CX1045]
AT93C46A@TSSOP8 [CX1059]	AT93C46C [CX0001]
AT93C46C@SOIC8 [CX1045]	AT93C46C@TSSOP8 [CX1059]
AT93C46D(08bit) [CX0001]	AT93C46D(08bit)@dBGA8 [CX5156]
AT93C46D(08bit)@MAP8 [CX4002]	AT93C46D(08bit)@SOIC8 [CX1045]
AT93C46D(08bit)@TSSOP8 [CX1059]	AT93C46D(16bit) [CX0001]
AT93C46D(16bit)@dBGA8 [CX5156]	AT93C46D(16bit)@MAP8 [CX4002]
AT93C46D(16bit)@SOIC8 [CX1045]	AT93C46D(16bit)@TSSOP8 [CX1059]
AT93C46E [CX0001]	AT93C46E@SOIC8 [CX1045]
AT93C46E@TSSOP8 [CX1059]	AT93C56(08bit) [CX0001]
AT93C56(08bit)@SOIC8 [CX1045]	AT93C56(16bit) [CX0001]
AT93C56(16bit)@SOIC8 [CX1045]	AT93C56A(08bit) [CX0001]
AT93C56A(08bit)@SOIC8 [CX1045]	AT93C56A(08bit)@TSSOP8 [CX1059]
AT93C56A(08bit)@UDFN8 [CX4002]	AT93C56A(16bit) [CX0001]
AT93C56A(16bit)@SOIC8 [CX1045]	AT93C56A(16bit)@TSSOP8 [CX1059]
AT93C56AW(08bit)@SOIC8 [CX1044]	AT93C56AW(16bit)@SOIC8 [CX1044]
AT93C56B(08bit) [CX0001]	AT93C56B(08bit)@SOIC8 [CX1045]
AT93C56B(08bit)@TSSOP8 [CX1059]	AT93C56B(08bit)@UDFN8 [CX4002]
AT93C56B(08bit)@VFBGA8 [CX5156]	AT93C56B(08bit)@XDFN8 [CX0001]
AT93C56B(16bit) [CX0001]	AT93C56B(16bit)@SOIC8 [CX1045]
AT93C56B(16bit)@TSSOP8 [CX1059]	AT93C56B(16bit)@UDFN8 [CX4002]
AT93C56B(16bit)@VFBGA8 [CX5156]	AT93C56B(16bit)@XDFN8 [CX0001]
AT93C57 [CX0001]	AT93C57@SOIC8 [CX1045]
AT93C66(08bit) [CX0001]	AT93C66(08bit)@SOIC8 [CX1045]
AT93C66(16bit) [CX0001]	AT93C66(16bit)@SOIC8 [CX1045]
AT93C66A(08bit) [CX0001]	AT93C66A(08bit)@SOIC8 [CX1045]
AT93C66A(08bit)@TSSOP8 [CX1059]	AT93C66A(16bit) [CX0001]
AT93C66A(16bit)@SOIC8 [CX1045]	AT93C66A(16bit)@TSSOP8 [CX1059]
AT93C66A(16bit)@UDFN8 [CX4002]	AT93C66AW(08bit)@SOIC8 [CX1044]
AT93C66AW(16bit)@SOIC8 [CX1044]	AT93C66B(08bit) [CX0001]
AT93C66B(08bit)@SOIC8 [CX1045]	AT93C66B(08bit)@TSSOP8 [CX1059]
AT93C66B(08bit)@UDFN8 [CX4002]	AT93C66B(08bit)@VFBGA8 [CX5156]
AT93C66B(08bit)@XDFN8 [CX0001]	AT93C66B(16bit) [CX0001]
AT93C66B(16bit)@SOIC8 [CX1045]	AT93C66B(16bit)@TSSOP8 [CX1059]
AT93C66B(16bit)@UDFN8 [CX4002]	AT93C66B(16bit)@VFBGA8 [CX5156]
AT93C66B(16bit)@XDFN8 [CX0001]	AT93C86(08bit) [CX0001]
AT93C86(08bit)@SOIC8 [CX1045]	AT93C86(08bit)@TSSOP8 [CX1059]
AT93C86(16bit) [CX0001]	AT93C86(16bit)@SOIC8 [CX1045]
AT93C86(16bit)@TSSOP8 [CX1059]	AT93C86A(08bit) [CX0001]
AT93C86A(08bit)@SOIC8 [CX1045]	AT93C86A(08bit)@TSSOP8 [CX1059]
AT93C86A(16bit) [CX0001]	AT93C86A(16bit)@SOIC8 [CX1045]
AT93C86A(16bit)@TSSOP8 [CX1059]	NS0001@SOIC8 [CX1016-2]

#### DRAM & SRAM

AT3864L [CX0001]	AT3864L@TSOP28 [CX1001]
AT38H256 [CX0001]	AT38H256@TSOP28 [CX1001]

#### PLD

ATF1500A@PLCC44 [CX2044]	ATF1500A@TQFP44 [CX3003]
ATF1500ABV@PLCC44 [CX2044]	ATF1500ABV@TQFP44 [CX3003]
ATF1500ABVL@PLCC44 [CX2044]	ATF1500ABVL@TQFP44 [CX3003]
ATF1500AL@PLCC44 [CX2044]	ATF1500AL@TQFP44 [CX3003]
ATF1502AS@PLCC44 [CX2044]	ATF1502AS@PQFP44 [CX3002]
ATF1502AS@TQFP44 [CX3003]	ATF1502ASL@PLCC44 [CX2044]
ATF1502ASL@PQFP44 [CX3002]	ATF1502ASL@TQFP44 [CX3003]

ATF1502ASV@PLCC44 [CX2044]  
ATF1502ASV@TQFP44 [CX3003]  
ATF1502ASVL@PQFP44 [CX3002]  
ATF1504AS@PLCC44 [CX2044]  
ATF16LV8C@PLCC20 [CX2020]  
ATF16LV8C@TSOP20 [CX1000]  
ATF16LV8CEXT@PLCC20 [CX2020]  
ATF16LV8CEXT@TSOP20 [CX1000]  
ATF16V8B@PLCC20 [CX2020]  
ATF16V8B@TSOP20 [CX1000]  
ATF16V8BL@PLCC20 [CX2020]  
ATF16V8BL@TSOP20 [CX1000]  
ATF16V8BQ@PLCC20 [CX2020]  
ATF16V8BQ@TSOP20 [CX1000]  
ATF16V8BQL@PLCC20 [CX2020]  
ATF16V8BQL@TSOP20 [CX1000]  
ATF16V8C@PLCC20 [CX2020]  
ATF16V8C@TSOP20 [CX1000]  
ATF16V8CEXT@PLCC20 [CX2020]  
ATF16V8CEXT@TSOP20 [CX1000]  
ATF16V8CZ@PLCC20 [CX2020]  
ATF16V8CZ@TSOP20 [CX1000]  
ATF20V8B@PLCC28 [CX2028]  
ATF20V8BL [CX0001]  
ATF20V8BL@SOIC24 [CX1003]  
ATF20V8BQ@PLCC28 [CX2028]  
ATF20V8BQL [CX0001]  
ATF20V8BQL@SOIC24 [CX1003]  
ATF22LV10C(UES) [CX0001]  
ATF22LV10C(UES)@SOIC24 [CX1033]  
ATF22LV10C@PLCC28 [CX2028]  
ATF22LV10C@TSSOP24 [CX1000]  
ATF22LV10CEXT@PLCC28 [CX2028]  
ATF22LV10CEXT@TSSOP24 [CX1000]  
ATF22LV10CQZ(UES) [CX0001]  
ATF22LV10CQZ(UES)@PLCC28 [CX2028]  
ATF22LV10CQZ(UES)@SOIC24 [CX1033]  
ATF22LV10CQZ(UES)@TSSOP24 [CX1000]  
ATF22LV10CQZ@PLCC28 [CX2028]  
ATF22LV10CQZ@TSSOP24 [CX1000]  
ATF22LV10CZ(UES) [CX0001]  
ATF22LV10CZ(UES)@SOIC24 [CX1033]  
ATF22LV10CZ(UES)@TSSOP24 [CX1000]  
ATF22LV10CZ@PLCC28 [CX2028]  
ATF22LV10CZ@TSSOP24 [CX1000]  
ATF22V10B@PLCC28 [CX2028]  
ATF22V10BL [CX0001]  
ATF22V10BL@SOIC24 [CX1033]  
ATF22V10BQ@PLCC28 [CX2028]  
ATF22V10BQL [CX0001]  
ATF22V10BQL@SOIC24 [CX1033]  
ATF22V10C(UES) [CX0001]  
ATF22V10C(UES)@SOIC24 [CX1033]  
ATF22V10C@PLCC28 [CX2028]  
ATF22V10C@TSSOP24 [CX1000]  
ATF22V10CEXT@PLCC28 [CX2028]  
ATF22V10CEXT@TSSOP24 [CX1000]  
ATF22V10CQ(UES) [CX0001]  
ATF22V10CQ(UES)@SOIC24 [CX1033]

ATF1502ASV@PQFP44 [CX3002]  
ATF1502ASVL@PLCC44 [CX2044]  
ATF1502ASVL@TQFP44 [CX3003]  
ATF16LV8C [CX0001]  
ATF16LV8C@SOIC20 [CX1033]  
ATF16LV8CEXT [CX0001]  
ATF16LV8CEXT@SOIC20 [CX1033]  
ATF16V8B [CX0001]  
ATF16V8B@SOIC20 [CX1033]  
ATF16V8BL [CX0001]  
ATF16V8BL@SOIC20 [CX1033]  
ATF16V8BQ [CX0001]  
ATF16V8BQ@SOIC20 [CX1033]  
ATF16V8BQL [CX0001]  
ATF16V8BQL@SOIC20 [CX1033]  
ATF16V8C [CX0001]  
ATF16V8C@SOIC20 [CX1033]  
ATF16V8CEXT [CX0001]  
ATF16V8CEXT@SOIC20 [CX1033]  
ATF16V8CZ [CX0001]  
ATF16V8CZ@SOIC20 [CX1033]  
ATF20V8B [CX0001]  
ATF20V8B@SOIC24 [CX1003]  
ATF20V8BL@PLCC28 [CX2028]  
ATF20V8BQ [CX0001]  
ATF20V8BQ@SOIC24 [CX1003]  
ATF20V8BQL@PLCC28 [CX2028]  
ATF22LV10C [CX0001]  
ATF22LV10C(UES)@PLCC28 [CX2028]  
ATF22LV10C(UES)@TSSOP24 [CX1000]  
ATF22LV10C@SOIC24 [CX1033]  
ATF22LV10CEXT [CX0001]  
ATF22LV10CEXT@SOIC24 [CX1033]  
ATF22LV10CQZ [CX0001]  
ATF22LV10CQZ@SOIC24 [CX1033]  
ATF22LV10CZ [CX0001]  
ATF22LV10CZ(UES)@PLCC28 [CX2028]  
ATF22LV10CZ@SOIC24 [CX1033]  
ATF22V10B [CX0001]  
ATF22V10B@SOIC24 [CX1033]  
ATF22V10BL@PLCC28 [CX2028]  
ATF22V10BQ [CX0001]  
ATF22V10BQ@SOIC24 [CX1033]  
ATF22V10BQL@PLCC28 [CX2028]  
ATF22V10C [CX0001]  
ATF22V10C(UES)@PLCC28 [CX2028]  
ATF22V10C(UES)@TSSOP24 [CX1000]  
ATF22V10C@SOIC24 [CX1033]  
ATF22V10CEXT [CX0001]  
ATF22V10CEXT@SOIC24 [CX1033]  
ATF22V10CQ [CX0001]  
ATF22V10CQ(UES)@PLCC28 [CX2028]  
ATF22V10CQ(UES)@TSSOP24 [CX1000]

ATF22V10CQ@PLCC28 [CX2028]  
ATF22V10CQ@TSSOP24 [CX1000]  
ATF22V10CQZ(UES) [CX0001]  
ATF22V10CQZ(UES)@SOIC24 [CX1033]  
ATF22V10CQZ(UES)@TSSOP24 [CX1000]  
ATF22V10CQZ@PLCC28 [CX2028]  
ATF22V10CQZ@TSSOP24 [CX1000]  
ATF22V10CZ(UES) [CX0001]  
ATF22V10CZ(UES)@SOIC24 [CX1033]  
ATF22V10CZ@PLCC28 [CX2028]  
ATF22V10CZ@TSSOP24 [CX1000]  
ATF2500C(F2500C)@PLCC44 [CX2044]  
ATF2500C(V2500) [CX0001]  
ATF2500C(V2500)@TQFP44 [CX3003]  
ATF2500C(V2500B)@PLCC44 [CX2044]  
ATF2500CL(F2500C) [CX0001]  
ATF2500CL(F2500C)@PLCC44 [CX2044]  
ATF2500CL(F2500C)@TQFP44 [CX3003]  
ATF2500CL(V2500) [CX0001]  
ATF2500CL(V2500)@TQFP44 [CX3003]  
ATF2500CL(V2500B)@PLCC44 [CX2044]  
ATF2500CL(V2500B)@TQFP44 [CX3003]  
ATF2500CQ(F2500C) [CX0001]  
ATF2500CQ(F2500C)@PLCC44 [CX2044]  
ATF2500CQ(F2500C)@TQFP44 [CX3003]  
ATF2500CQ(V2500B) [CX0001]  
ATF2500CQ(V2500B)@PLCC44 [CX2044]  
ATF2500CQ(V2500B)@TQFP44 [CX3003]  
ATF2500CQL(F2500C) [CX0001]  
ATF2500CQL(F2500C)@PLCC44 [CX2044]  
ATF2500CQL(F2500C)@TQFP44 [CX3003]  
ATF2500CQL(V2500B) [CX0001]  
ATF2500CQL(V2500B)@PLCC44 [CX2044]  
ATF2500CQL(V2500B)@TQFP44 [CX3003]  
ATV2500 [CX0001]  
ATV2500B [CX0001]  
ATV2500BL [CX0001]  
ATV2500BQ [CX0001]  
ATV2500BQL [CX0001]  
ATV2500H [CX0001]  
ATV2500L [CX0001]  
ATV750 [CX0001]  
ATV750@SOIC24 [CX1033]  
ATV750B@PLCC28 [CX2028]  
ATV750BL [CX0001]  
ATV750BL@SOIC24 [CX1033]  
ATV750L@PLCC28 [CX2028]  
ATF22V10CQ@SOIC24 [CX1033]  
ATF22V10CQZ [CX0001]  
ATF22V10CQZ(UES)@PLCC28 [CX2028]  
ATF22V10CQZ@SOIC24 [CX1033]  
ATF22V10CZ [CX0001]  
ATF22V10CZ(UES)@PLCC28 [CX2028]  
ATF22V10CZ(UES)@TSSOP24 [CX1000]  
ATF22V10CZ@SOIC24 [CX1033]  
ATF2500C(F2500C) [CX0001]  
ATF2500C(F2500C)@TQFP44 [CX3003]  
ATF2500C(V2500)@PLCC44 [CX2044]  
ATF2500C(V2500B) [CX0001]  
ATF2500C(V2500B)@TQFP44 [CX3003]  
ATF2500CL(V2500)@PLCC44 [CX2044]  
ATF2500CL(V2500B) [CX0001]  
ATV2500@PLCC44 [CX2044]  
ATV2500B@PLCC44 [CX2044]  
ATV2500BL@PLCC44 [CX2044]  
ATV2500BQ@PLCC44 [CX2044]  
ATV2500BQL@PLCC44 [CX2044]  
ATV2500H@PLCC44 [CX2044]  
ATV2500L@PLCC44 [CX2044]  
ATV750@PLCC28 [CX2028]  
ATV750B [CX0001]  
ATV750B@SOIC24 [CX1033]  
ATV750BL@PLCC28 [CX2028]  
ATV750L [CX0001]  
ATV750L@SOIC24 [CX1033]

## MICROCONTROLLER

AT32UC3A0128@TQFP144(ISP) [CX0001]  
AT32UC3A0256@TQFP144(ISP) [CX0001]  
AT32UC3A0512@TQFP144(ISP) [CX0001]  
AT32UC3A1128@TQFP100 [CX3021]  
AT32UC3A1128@TQFP100(ISP) [CX0001]  
AT32UC3A1256@TQFP100 [CX3021]  
AT32UC3A1256@TQFP100(ISP) [CX0001]  
AT32UC3A1512@TQFP100 [CX3021]  
AT32UC3A1512@TQFP100(ISP) [CX0001]

AT32UC3B0128@QFN64 [CX4023]  
AT32UC3B0128@TQFP64 [CX3011]  
AT32UC3B0128@TQFP64(ISP) [CX0001]  
AT32UC3B0256@QFN64 [CX4023]  
AT32UC3B0256@TQFP64 [CX3011]  
AT32UC3B0256@TQFP64(ISP) [CX0001]  
AT32UC3B0512@QFN64 [CX4023]  
AT32UC3B064@QFN64 [CX4023]  
AT32UC3B064@TQFP64 [CX3011]  
AT32UC3B1128@QFN48 [CX4021]  
AT32UC3B1128@TQFP48 [CX3007]  
AT32UC3B1128@TQFP48(ISP) [CX0001]  
AT32UC3B1256@QFN48 [CX4021]  
AT32UC3B1256@TQFP48 [CX3007]  
AT32UC3B1256@TQFP48(ISP) [CX0001]  
AT32UC3B1512@QFN48 [CX4021]  
AT32UC3B164@QFN48 [CX4021]  
AT32UC3B164@TQFP48 [CX3007]  
AT32UC3C1128C@TQFP100 [CX3043]  
AT32UC3C1512C@TQFP100 [CX3043]  
AT32UC3C2128C@QFN64 [CX4023]  
AT32UC3C2256C@QFN64 [CX4023]  
AT32UC3C2512C@QFN64 [CX4023]  
AT32UC3C264C@QFN64 [CX4023]  
AT32UC3L016@QFN48 [CX4021]  
AT32UC3L032@QFN48 [CX4021]  
AT32UC3L064@QFN48 [CX4021]  
AT80F51 [CX0001]  
AT80F51@TQFP44 [CX3003]  
AT80F52@PLCC44 [CX2044]  
AT87C51RB2 [CX0001]  
AT87C51RB2@TQFP44 [CX3002]  
AT87C51RC2@PLCC44 [CX2044]  
AT87C51RD2 [CX0001]  
AT87C51RD2@TQFP44 [CX3002]  
AT87C51U2@PLCC44 [CX2044]  
AT87C52X2 [CX0001]  
AT87C52X2@TQFP44 [CX3002]  
AT87C54X2@PLCC44 [CX2044]  
AT87C58X2 [CX0001]  
AT87C58X2@TQFP44 [CX3002]  
AT87F51@PLCC44 [CX2044]  
AT87F51RC [CX0001]  
AT87F51RC@TQFP44 [CX3002]  
AT87F52@PLCC44 [CX2044]  
AT87F55 [CX0001]  
AT87F55@TQFP44 [CX3002]  
AT87F55WD@PLCC44 [CX2044]  
AT87LV51 [CX0001]  
AT87LV51@TQFP44 [CX3002]  
AT87LV52@PLCC44 [CX2044]  
AT89C1051 [CX0001]  
AT89C1051U [CX0001]  
AT89C2051 [CX0001]  
AT89C2051X2 [CX0001]  
AT89C4051 [CX0001]  
AT89C51 [CX0001]  
AT89C51@PQFP44 [CX3002]  
AT89C5130A@PLCC52 [CX2052]

AT32UC3B0128@QFN64(ISP) [CX0001]  
AT32UC3B0256@QFN64(ISP) [CX0001]  
AT32UC3B0512@TQFP64 [CX3011]  
AT32UC3B064@QFN64(ISP) [CX0001]  
AT32UC3B064@TQFP64(ISP) [CX0001]  
AT32UC3B1128@QFN48(ISP) [CX0001]  
AT32UC3B1256@QFN48(ISP) [CX0001]  
AT32UC3B1512@TQFP48 [CX3007]  
AT32UC3B164@QFN48(ISP) [CX0001]  
AT32UC3B164@TQFP48(ISP) [CX0001]  
AT32UC3C1256C@TQFP100 [CX3043]  
AT32UC3C164C@TQFP100 [CX3043]  
AT32UC3C2128C@TQFP64 [CX3011]  
AT32UC3C2256C@TQFP64 [CX3011]  
AT32UC3C2512C@TQFP64 [CX3011]  
AT32UC3C264C@TQFP64 [CX3011]  
AT32UC3L016@TQFP48 [CX3007]  
AT32UC3L032@TQFP48 [CX3007]  
AT32UC3L064@TQFP48 [CX3007]  
AT80F51@PLCC44 [CX2044]  
AT80F52 [CX0001]  
AT80F52@TQFP44 [CX3003]  
AT87C51RB2@PLCC44 [CX2044]  
AT87C51RC2 [CX0001]  
AT87C51RC2@TQFP44 [CX3002]  
AT87C51RD2@PLCC44 [CX2044]  
AT87C51U2 [CX0001]  
AT87C51U2@TQFP44 [CX3002]  
AT87C52X2@PLCC44 [CX2044]  
AT87C54X2 [CX0001]  
AT87C54X2@TQFP44 [CX3002]  
AT87C58X2@PLCC44 [CX2044]  
AT87F51 [CX0001]  
AT87F51@TQFP44 [CX3002]  
AT87F51RC@PLCC44 [CX2044]  
AT87F52 [CX0001]  
AT87F52@TQFP44 [CX3002]  
AT87F55@PLCC44 [CX2044]  
AT87F55WD [CX0001]  
AT87F55WD@TQFP44 [CX3002]  
AT87LV51@PLCC44 [CX2044]  
AT87LV52 [CX0001]  
AT87LV52@TQFP44 [CX3002]  
AT89C1051@SOIC20 [CX1033]  
AT89C1051U@SOIC20 [CX1033]  
AT89C2051@SOIC20 [CX1033]  
AT89C2051X2@SOIC20 [CX1033]  
AT89C4051@SOIC20 [CX1033]  
AT89C51@PLCC44 [CX2044]  
AT89C51@TQFP44 [CX3003]  
AT89C5130A@QFN32 [CX4016]

AT89C5130A@SOIC28 [CX1033]  
AT89C5130AM@PLCC52 [CX2052]  
AT89C5130AM@SOIC28 [CX1033]  
AT89C5131@MLF48 [CX4021]  
AT89C5131@SOIC28 [CX1033]  
AT89C5131A@PLCC52 [CX2052]  
AT89C5131A@SOIC28 [CX1033]  
AT89C5131AL@PLCC52 [CX2052]  
AT89C5131AL@SOIC28 [CX1033]  
AT89C5131AM@PLCC52 [CX2052]  
AT89C5131AM@SOIC28 [CX1033]  
AT89C5132@TQFP80 [CX3018]  
AT89C51AC2@TQFP44 [CX3003]  
AT89C51AC3@PLCC52 [CX2052]  
AT89C51AC3@TQFP64 [CX3011]  
AT89C51CC01@TQFP44 [CX3003]  
AT89C51CC03C@PLCC52 [CX2052]  
AT89C51CC03C@TQFP64 [CX3011]  
AT89C51CC03CA@PLCC52 [CX2052]  
AT89C51CC03CA@TQFP64 [CX3011]  
AT89C51CC03U@PLCC52 [CX2052]  
AT89C51CC03U@TQFP64 [CX3011]  
AT89C51CC03UA@PLCC52 [CX2052]  
AT89C51CC03UA@TQFP64 [CX3011]  
AT89C51ED2@PLCC44 [CX2044]  
AT89C51ED2@TQFP44 [CX3005]  
AT89C51IC2@PLCC44 [CX2044]  
AT89C51ID2 [CX0001]  
AT89C51ID2@PLCC68 [CX2068]  
AT89C51ID2@TQFP64 [CX3011]  
AT89C51RB2@PLCC44 [CX2044]  
AT89C51RC [CX0001]  
AT89C51RC@TQFP44 [CX3003]  
AT89C51RC2@PLCC44 [CX2044]  
AT89C51RD2 [CX0001]  
AT89C51RD2@PLCC68 [CX2068]  
AT89C51RD2@PLCC68(\*) [SA648-B6808]  
AT89C51RD2@TQFP44 [CX3005]  
AT89C51RD2@TQFP64(\*) [TA054-B006]  
AT89C51RE2@PLCC44 [CX2044]  
AT89C51RE2@VQFP64 [CX3011]  
AT89C51SND1C@PLCC84 [CX2084]  
AT89C51SND2C@BGA100 [CX5055]  
AT89C52@PLCC44 [CX2044]  
AT89C52@TQFP44 [CX3003]  
AT89C55@PLCC44 [CX2044]  
AT89C55@TQFP44 [CX3003]  
AT89C55WD@PLCC44 [CX2044]  
AT89LP2051 [CX0001]  
AT89LP2051@TSSOP20 [CX1000]  
AT89LP2052(ISP) [CX0001]  
AT89LP2052@SOIC20(ISP) [CX0001]  
AT89LP2052@TSSOP20(ISP) [CX0001]  
AT89LP213(ISP) [CX0001]  
AT89LP213@TSSOP14(ISP) [CX0001]  
AT89LP214(ISP) [CX0001]  
AT89LP214@TSSOP14(ISP) [CX0001]  
AT89LP216(ISP) [CX0001]  
AT89LP216@SOIC16(ISP) [CX0001]

AT89C5130A@VQFP64 [CX3011]  
AT89C5130AM@QFN32 [CX4016]  
AT89C5130AM@VQFP64 [CX3011]  
AT89C5131@PLCC52 [CX2052]  
AT89C5131@VQFP64 [CX3011]  
AT89C5131A@QFN32 [CX4016]  
AT89C5131A@VQFP64 [CX3011]  
AT89C5131AL@QFN32 [CX4016]  
AT89C5131AL@VQFP64 [CX3011]  
AT89C5131AM@QFN32 [CX4016]  
AT89C5131AM@VQFP64 [CX3011]  
AT89C51AC2@PLCC44 [CX2044]  
AT89C51AC3@PLCC44 [CX2044]  
AT89C51AC3@TQFP44 [CX3003]  
AT89C51CC01@PLCC44 [CX2044]  
AT89C51CC03C@PLCC44 [CX2044]  
AT89C51CC03C@TQFP44 [CX3003]  
AT89C51CC03CA@PLCC44 [CX2044]  
AT89C51CC03CA@TQFP44 [CX3003]  
AT89C51CC03U@PLCC44 [CX2044]  
AT89C51CC03U@TQFP44 [CX3003]  
AT89C51CC03UA@PLCC44 [CX2044]  
AT89C51CC03UA@TQFP44 [CX3003]  
AT89C51ED2 [CX0001]  
AT89C51ED2@PLCC68 [CX2068]  
AT89C51ED2@TQFP64 [CX3011]  
AT89C51IC2@TQFP44 [CX3003]  
AT89C51ID2@PLCC44 [CX2044]  
AT89C51ID2@TQFP44 [CX3005]  
AT89C51RB2 [CX0001]  
AT89C51RB2@TQFP44 [CX3003]  
AT89C51RC@PLCC44 [CX2044]  
AT89C51RC2 [CX0001]  
AT89C51RC2@TQFP44 [CX3003]  
AT89C51RD2@PLCC44 [CX2044]  
AT89C51RD2@TQFP64 [CX3011]  
AT89C51RE2@VQFP44 [CX3005]  
AT89C51SND1C@BGA81 [CX5071]  
AT89C51SND1C@TQFP80 [CX3018]  
AT89C52 [CX0001]  
AT89C52@PQFP44 [CX3002]  
AT89C55 [CX0001]  
AT89C55@PQFP44 [CX3002]  
AT89C55WD [CX0001]  
AT89C55WD@TQFP44 [CX3003]  
AT89LP2051@SOIC20 [CX1033]  
AT89LP2052 [CX0001]  
AT89LP2052@SOIC20 [CX1033]  
AT89LP2052@TSSOP20 [CX1000]  
AT89LP213 [CX0001]  
AT89LP213@TSSOP14 [CX1026]  
AT89LP214 [CX0001]  
AT89LP214@TSSOP14 [CX1026]  
AT89LP216 [CX0001]  
AT89LP216@SOIC16 [CX1033]  
AT89LP216@TSSOP16 [CX1026]

AT89LP216@TSSOP16(ISP) [CX0001]  
AT89LP3240(ISP) [CX0001]  
AT89LP3240@MLF44(ISP) [CX0001]  
AT89LP3240@PLCC44(ISP) [CX0001]  
AT89LP3240@TQFP44(ISP) [CX0001]  
AT89LP4051@SOIC20 [CX1033]  
AT89LP4052 [CX0001]  
AT89LP4052@SOIC20 [CX1033]  
AT89LP4052@TSSOP20 [CX1000]  
AT89LP428 [CX0001]  
AT89LP428@PLCC32 [CX2032]  
AT89LP428@TQFP32 [CX3001]  
AT89LP51 [CX0001]  
AT89LP51@TQFP44 [CX3003]  
AT89LP51ED2(isp) [CX0001]  
AT89LP51ED2@PLCC44 [CX2044]  
AT89LP51ID2 [CX0001]  
AT89LP51ID2@MLF44 [CX4018]  
AT89LP51ID2@TQFP44 [CX3003]  
AT89LP51RB2(isp) [CX0001]  
AT89LP51RB2@PLCC44 [CX2044]  
AT89LP51RC2 [CX0001]  
AT89LP51RC2@MLF44 [CX4018]  
AT89LP51RC2@TQFP44 [CX3003]  
AT89LP51RD2(isp) [CX0001]  
AT89LP51RD2@PLCC44 [CX2044]  
AT89LP52 [CX0001]  
AT89LP52@TQFP44 [CX3003]  
AT89LP6440(ISP) [CX0001]  
AT89LP6440@MLF44(ISP) [CX0001]  
AT89LP6440@PLCC44(ISP) [CX0001]  
AT89LP6440@TQFP44(ISP) [CX0001]  
AT89LP828(ISP) [CX0001]  
AT89LP828@PLCC32(ISP) [CX0001]  
AT89LP828@TQFP32(ISP) [CX0001]  
AT89LS51(ISP) [CX0001]  
AT89LS51@PLCC44(ISP) [CX0001]  
AT89LS51@TQFP44(ISP) [CX0001]  
AT89LS52(ISP) [CX0001]  
AT89LS52@PLCC44(ISP) [CX0001]  
AT89LS52@TQFP44(ISP) [CX0001]  
AT89LS53(ISP) [CX0001]  
AT89LS53@PLCC44(ISP) [CX0001]  
AT89LS53@TQFP44(ISP) [CX0001]  
AT89LS8252(ISP) [CX0001]  
AT89LS8252@PLCC44(ISP) [CX0001]  
AT89LS8252@TQFP44(ISP) [CX0001]  
AT89LV51@PLCC44 [CX2044]  
AT89LV52 [CX0001]  
AT89LV52@TQFP44 [CX3003]  
AT89LV55@PLCC44 [CX2044]  
AT89S2051 [CX0001]  
AT89S4051 [CX0001]  
AT89S51 [CX0001]  
AT89S51@PLCC44 [CX2044]  
AT89S51@TQFP44 [CX3003]  
AT89S52 [CX0001]  
AT89S52@PLCC44 [CX2044]  
AT89S52@TQFP44 [CX3003]

AT89LP3240 [CX0001]  
AT89LP3240@MLF44 [CX4018]  
AT89LP3240@PLCC44 [CX2044]  
AT89LP3240@TQFP44 [CX3005]  
AT89LP4051 [CX0001]  
AT89LP4051@TSSOP20 [CX1000]  
AT89LP4052(ISP) [CX0001]  
AT89LP4052@SOIC20(ISP) [CX0001]  
AT89LP4052@TSSOP20(ISP) [CX0001]  
AT89LP428(ISP) [CX0001]  
AT89LP428@PLCC32(ISP) [CX0001]  
AT89LP428@TQFP32(ISP) [CX0001]  
AT89LP51@PLCC44 [CX2044]  
AT89LP51ED2 [CX0001]  
AT89LP51ED2@MLF44 [CX4018]  
AT89LP51ED2@TQFP44 [CX3003]  
AT89LP51ID2(isp) [CX0001]  
AT89LP51ID2@PLCC44 [CX2044]  
AT89LP51RB2 [CX0001]  
AT89LP51RB2@MLF44 [CX4018]  
AT89LP51RB2@TQFP44 [CX3003]  
AT89LP51RC2(isp) [CX0001]  
AT89LP51RC2@PLCC44 [CX2044]  
AT89LP51RD2 [CX0001]  
AT89LP51RD2@MLF44 [CX4018]  
AT89LP51RD2@TQFP44 [CX3003]  
AT89LP52@PLCC44 [CX2044]  
AT89LP6440 [CX0001]  
AT89LP6440@MLF44 [CX4018]  
AT89LP6440@PLCC44 [CX2044]  
AT89LP6440@TQFP44 [CX3005]  
AT89LP828 [CX0001]  
AT89LP828@PLCC32 [CX2032]  
AT89LP828@TQFP32 [CX3001]  
AT89LS51 [CX0001]  
AT89LS51@PLCC44 [CX2044]  
AT89LS51@TQFP44 [CX3003]  
AT89LS52 [CX0001]  
AT89LS52@PLCC44 [CX2044]  
AT89LS52@TQFP44 [CX3003]  
AT89LS53 [CX0001]  
AT89LS53@PLCC44 [CX2044]  
AT89LS53@TQFP44 [CX3003]  
AT89LS8252 [CX0001]  
AT89LS8252@PLCC44 [CX2044]  
AT89LS8252@TQFP44 [CX3003]  
AT89LV51 [CX0001]  
AT89LV51@TQFP44 [CX3003]  
AT89LV52@PLCC44 [CX2044]  
AT89LV55 [CX0001]  
AT89LV55@TQFP44 [CX3003]  
AT89S2051@SOIC20 [CX1033]  
AT89S4051@SOIC20 [CX1033]  
AT89S51(ISP) [CX0001]  
AT89S51@PLCC44(ISP) [CX0001]  
AT89S51@TQFP44(ISP) [CX0001]  
AT89S52(ISP) [CX0001]  
AT89S52@PLCC44(ISP) [CX0001]  
AT89S52@TQFP44(ISP) [CX0001]

AT89S53 [CX0001]  
AT89S53@PLCC44 [CX2044]  
AT89S53@TQFP44 [CX3003]  
AT89S54 [CX0001]  
AT89S54@TQFP44 [CX3003]  
AT89S58@PLCC44 [CX2044]  
AT89S64 [CX0001]  
AT89S64@TQFP44 [CX3005]  
AT89S8252(ISP) [CX0001]  
AT89S8252@PLCC44(ISP) [CX0001]  
AT89S8252@TQFP44 [CX3003]  
AT89S8253 [CX0001]  
AT89S8253@TQFP44 [CX3003]  
AT90CAN128@TQFP64 [CX3013]  
AT90CAN32@TQFP64 [CX3013]  
AT90CAN64@TQFP64 [CX3013]  
AT90LS2323@SOIC8 [CX1044]  
AT90LS2333@TQFP32 [CX3001]  
AT90LS2343@SOIC8 [CX1044]  
AT90LS4433@TQFP32 [CX3001]  
AT90LS4434@PLCC44 [CX2044]  
AT90LS8535 [CX0001]  
AT90LS8535@TQFP44 [CX3003]  
AT90PWM161@QFN32 [CX4015]  
AT90PWM2@SOIC24 [CX1033]  
AT90PWM2B@SOIC24 [CX1033]  
AT90PWM3@SOIC32 [CX1069]  
AT90PWM316@SOIC32 [CX1069]  
AT90PWM3B@SOIC32 [CX1069]  
AT90PWM81@SOIC20 [CX1033]  
AT90S1200@SOIC20 [CX1033]  
AT90S1200A [CX0001]  
AT90S1200A@SSOP20 [CX1026]  
AT90S2313@SOIC20 [CX1033]  
AT90S2323@SOIC8 [CX1044]  
AT90S2333@TQFP32 [CX3001]  
AT90S2343@SOIC8 [CX1044]  
AT90S4414@PLCC44 [CX2044]  
AT90S4433 [CX0001]  
AT90S4434 [CX0001]  
AT90S4434@TQFP44 [CX3003]  
AT90S8515@PLCC44 [CX2044]  
AT90S8535 [CX0001]  
AT90S8535@TQFP44 [CX3003]  
AT90USB1286@TQFP64 [CX3013]  
AT90USB1287@TQFP64 [CX3013]  
AT90USB162@QFN32(ISP) [CX0001]  
AT90USB162@VQFP32(ISP) [CX0001]  
AT90USB646@TQFP64 [CX3013]  
AT90USB647@TQFP64 [CX3013]  
AT90USB82@QFN32(ISP) [CX0001]  
AT91SAM7S128@QFN64 [CX4023]  
AT91SAM7S16@QFN48 [CX4021]  
AT91SAM7S161@QFN64 [CX4023]  
AT91SAM7S256@QFN64 [CX4023]  
AT91SAM7S32@QFN48 [CX4021]  
AT91SAM7S321@QFN64 [CX4023]  
AT91SAM7S512@QFN64 [CX4023]  
AT91SAM7S64@QFN64 [CX4023]

AT89S53(ISP) [CX0001]  
AT89S53@PLCC44(ISP) [CX0001]  
AT89S53@TQFP44(ISP) [CX0001]  
AT89S54@PLCC44 [CX2044]  
AT89S58 [CX0001]  
AT89S58@TQFP44 [CX3003]  
AT89S64@PLCC44 [CX2044]  
AT89S8252 [CX0001]  
AT89S8252@PLCC44 [CX2044]  
AT89S8252@PQFP44 [CX3002]  
AT89S8252@TQFP44(ISP) [CX0001]  
AT89S8253@PLCC44 [CX2044]  
AT90CAN128@QFN64 [CX4023]  
AT90CAN32@QFN64 [CX4023]  
AT90CAN64@QFN64 [CX4023]  
AT90LS2323 [CX0001]  
AT90LS2333 [CX0001]  
AT90LS2343 [CX0001]  
AT90LS4433 [CX0001]  
AT90LS4434 [CX0001]  
AT90LS4434@TQFP44 [CX3003]  
AT90LS8535@PLCC44 [CX2044]  
AT90PWM1@SOIC24 [CX1033]  
AT90PWM161@SOIC20 [CX1033]  
AT90PWM216@SOIC24 [CX1033]  
AT90PWM3@QFN32 [CX4016]  
AT90PWM316@QFN32 [CX4016]  
AT90PWM3B@QFN32 [CX4016]  
AT90PWM81@QFN32 [CX4030]  
AT90S1200 [CX0001]  
AT90S1200@SSOP20 [CX1026]  
AT90S1200A@SOIC20 [CX1033]  
AT90S2313 [CX0001]  
AT90S2323 [CX0001]  
AT90S2333 [CX0001]  
AT90S2343 [CX0001]  
AT90S4414 [CX0001]  
AT90S4414@TQFP44 [CX3003]  
AT90S4433@TQFP32 [CX3001]  
AT90S4434@PLCC44 [CX2044]  
AT90S8515 [CX0001]  
AT90S8515@TQFP44 [CX3003]  
AT90S8535@PLCC44 [CX2044]  
AT90USB1286@QFN64 [CX4023]  
AT90USB1287@QFN64 [CX4023]  
AT90USB162@QFN32 [CX4015]  
AT90USB162@VQFP32 [CX3001]  
AT90USB646@QFN64 [CX4023]  
AT90USB647@QFN64 [CX4023]  
AT90USB82@QFN32 [CX4015]  
AT91SAM7S128@LQFP64 [CX3011]  
AT91SAM7S16@LQFP48 [CX3007]  
AT91SAM7S161@LQFP64 [CX3011]  
AT91SAM7S256@LQFP64 [CX3011]  
AT91SAM7S32@LQFP48 [CX3007]  
AT91SAM7S321@LQFP64 [CX3011]  
AT91SAM7S512@LQFP64 [CX3011]  
AT91SAM7S64@LQFP64 [CX3011]  
AT91SAM7S64B@LQFP64 [CX3011]

ATA5780@VQFN32 [CX4015]  
ATA5830@VQFN32 [CX4015]  
ATC71RBX2 [CX0001]  
ATC71RBX2@TQFP44 [CX3002]  
ATC71RCX2@PLCC44 [CX2044]  
ATC71RDX2 [CX0001]  
ATC71RDX2@PLCC68 [CX2068]  
ATC71RDX2@TQFP64 [CX3012]  
ATC87C51@PLCC44 [CX2044]  
ATC87C52 [CX0001]  
ATC87C52@TQFP44 [CX3002]  
ATC87C54@PLCC44 [CX2044]  
ATC87C58 [CX0001]  
ATC87C58@TQFP44 [CX3002]  
ATMEGA103L@TQFP64 [CX3013]  
ATMEGA128@MLF64(ISP) [CX0001]  
ATMEGA128@TQFP64(ISP) [CX0001]  
ATMEGA1280@CBGA100(ISP) [CX0001]  
ATMEGA1280@TQFP100(ISP) [CX0001]  
ATMEGA1280V@CBGA100(ISP) [CX0001]  
ATMEGA1280V@TQFP100 [CX3043]  
ATMEGA1280V@TQFP100(ISP) [CX0001]  
ATMEGA1281@MLF64 [CX4023]  
ATMEGA1281@TQFP64 [CX3013]  
ATMEGA1281V@MLF64 [CX4023]  
ATMEGA1281V@TQFP64 [CX3013]  
ATMEGA1284 [CX0001]  
ATMEGA1284@MLF44 [CX4018]  
ATMEGA1284@TQFP44 [CX3003]  
ATMEGA1284P [CX0001]  
ATMEGA1284P@MLF44 [CX4018]  
ATMEGA1284P@TQFP44 [CX3003]  
ATMEGA1284PV [CX0001]  
ATMEGA1284PV@MLF44 [CX4018]  
ATMEGA1284PV@TQFP44 [CX3003]  
ATMEGA1284PV@TQFP44(ISP) [CX0001]  
ATMEGA128A@MLF64 [CX4023]  
ATMEGA128L@MLF64 [CX4023]  
ATMEGA128L@TQFP64 [CX3013]  
ATMEGA128RFA1@MLF64 [CX4023]  
ATMEGA16 [CX0001]  
ATMEGA16@TQFP44 [CX3005]  
ATMEGA161@TQFP44 [CX3002]  
ATMEGA161L@TQFP44 [CX3002]  
ATMEGA162(ISP) [CX0001]  
ATMEGA162@MLF44(ISP) [CX0001]  
ATMEGA162@TQFP44(ISP) [CX0001]  
ATMEGA162V(ISP) [CX0001]  
ATMEGA162V@MLF44(ISP) [CX0001]  
ATMEGA162V@TQFP44(ISP) [CX0001]  
ATMEGA163@TQFP44 [CX3002]  
ATMEGA163L@TQFP44 [CX3002]  
ATMEGA164(ISP) [CX0001]  
ATMEGA164@MLF44(ISP) [CX0001]  
ATMEGA164@TQFP44(ISP) [CX0001]  
ATMEGA164A(ISP) [CX0001]  
ATMEGA164A@MLF44(ISP) [CX0001]  
ATMEGA164A@TQFP44(ISP) [CX0001]  
ATMEGA164A@VFPGA49(ISP) [CX0001]

ATA5780N@VQFN32 [CX4015]  
ATA5830N@VQFN32 [CX4015]  
ATC71RBX2@PLCC44 [CX2044]  
ATC71RCX2 [CX0001]  
ATC71RCX2@TQFP44 [CX3002]  
ATC71RDX2@PLCC44 [CX2044]  
ATC71RDX2@TQFP44 [CX3002]  
ATC87C51 [CX0001]  
ATC87C51@TQFP44 [CX3002]  
ATC87C52@PLCC44 [CX2044]  
ATC87C54 [CX0001]  
ATC87C54@TQFP44 [CX3002]  
ATC87C58@PLCC44 [CX2044]  
ATMEGA103@TQFP64 [CX3013]  
ATMEGA128@MLF64 [CX4023]  
ATMEGA128@TQFP64 [CX3013]  
ATMEGA1280@CBGA100 [CX5055]  
ATMEGA1280@TQFP100 [CX3043]  
ATMEGA1280V@CBGA100 [CX5055]  
ATMEGA1281@MLF64(ISP) [CX0001]  
ATMEGA1281@TQFP64(ISP) [CX0001]  
ATMEGA1281V@MLF64(ISP) [CX0001]  
ATMEGA1281V@TQFP64(ISP) [CX0001]  
ATMEGA1284(ISP) [CX0001]  
ATMEGA1284@MLF44(ISP) [CX0001]  
ATMEGA1284@TQFP44(ISP) [CX0001]  
ATMEGA1284P(ISP) [CX0001]  
ATMEGA1284P@MLF44(ISP) [CX0001]  
ATMEGA1284P@TQFP44(ISP) [CX0001]  
ATMEGA1284PV(ISP) [CX0001]  
ATMEGA1284PV@MLF44(ISP) [CX0001]  
ATMEGA128A@TQFP64 [CX3013]  
ATMEGA128L@MLF64(ISP) [CX0001]  
ATMEGA128L@TQFP64(ISP) [CX0001]  
ATMEGA128RFR2@QFN64 [CX4023]  
ATMEGA16@MLF44 [CX4018]  
ATMEGA161 [CX0001]  
ATMEGA161L [CX0001]  
ATMEGA162 [CX0001]  
ATMEGA162@MLF44 [CX4018]  
ATMEGA162@TQFP44 [CX3003]  
ATMEGA162V [CX0001]  
ATMEGA162V@MLF44 [CX4018]  
ATMEGA162V@TQFP44 [CX3003]  
ATMEGA163 [CX0001]  
ATMEGA163L [CX0001]  
ATMEGA164 [CX0001]  
ATMEGA164@MLF44 [CX4018]  
ATMEGA164@TQFP44 [CX3005]  
ATMEGA164A [CX0001]  
ATMEGA164A@MLF44 [CX4018]  
ATMEGA164A@TQFP44 [CX3003]  
ATMEGA164A@VFPGA49 [CX4018]  
ATMEGA164P [CX0001]



ATMEGA164P(ISP) [CX0001]  
ATMEGA164P@MLF44(ISP) [CX0001]  
ATMEGA164P@TQFP44(ISP) [CX0001]  
ATMEGA164PA(ISP) [CX0001]  
ATMEGA164PA@MLF44(ISP) [CX0001]  
ATMEGA164PA@TQFP44(ISP) [CX0001]  
ATMEGA164PA@VFBGA49(ISP) [CX0001]  
ATMEGA164PV [CX0001]  
ATMEGA164PV@MLF44 [CX4018]  
ATMEGA164PV@TQFP44 [CX3005]  
ATMEGA164V [CX0001]  
ATMEGA164V@MLF44 [CX4018]  
ATMEGA164V@TQFP44 [CX3005]  
ATMEGA165@MLF64 [CX4023]  
ATMEGA165A@MLF64 [CX4023]  
ATMEGA165PA@MLF64 [CX4023]  
ATMEGA165V@MLF64 [CX4023]  
ATMEGA168 [CX0001]  
ATMEGA168@MLF28 [CX4033]  
ATMEGA168@MLP28(ISP) [CX0001]  
ATMEGA168@TQFP32 [CX3001]  
ATMEGA168A [CX0001]  
ATMEGA168A@MLF32 [CX4015]  
ATMEGA168P [CX0001]  
ATMEGA168P@MLF28 [CX4033]  
ATMEGA168P@MLP28(ISP) [CX0001]  
ATMEGA168P@TQFP32 [CX3001]  
ATMEGA168PA [CX0001]  
ATMEGA168PA@MLF32 [CX4015]  
ATMEGA168PV [CX0001]  
ATMEGA168PV@MLF28 [CX4033]  
ATMEGA168PV@MLP28(ISP) [CX0001]  
ATMEGA168PV@TQFP32 [CX3001]  
ATMEGA168V [CX0001]  
ATMEGA168V@MLF28 [CX4033]  
ATMEGA168V@MLP28(ISP) [CX0001]  
ATMEGA168V@TQFP32 [CX3001]  
ATMEGA169@MLF64 [CX4023]  
ATMEGA169@TQFP64 [CX3013]  
ATMEGA169P@MLF64 [CX4023]  
ATMEGA169P@TQFP64 [CX3013]  
ATMEGA169PV@MLF64 [CX4023]  
ATMEGA169PV@TQFP64 [CX3013]  
ATMEGA169V@MLF64 [CX4023]  
ATMEGA169V@TQFP64 [CX3013]  
ATMEGA16A [CX0001]  
ATMEGA16A@TQFP44 [CX3005]  
ATMEGA16HVA@TSOP28(ISP) [CX0001]  
ATMEGA16L [CX0001]  
ATMEGA16L@TQFP44 [CX3005]  
ATMEGA16M1@MLF32(ISP) [CX0001]  
ATMEGA16M1@TQFP32(ISP) [CX0001]  
ATMEGA16U2@VQFP32 [CX3001]  
ATMEGA16U4@MLF44(ISP) [CX0001]  
ATMEGA16U4@TQFP44(ISP) [CX0001]  
ATMEGA2560@CBGA100(ISP) [CX0001]  
ATMEGA2560@TQFP100(ISP) [CX0001]  
ATMEGA2560V@CBGA100(ISP) [CX0001]  
ATMEGA2560V@TQFP100 [CX3043]  
ATMEGA164P@MLF44 [CX4018]  
ATMEGA164P@TQFP44 [CX3005]  
ATMEGA164PA [CX0001]  
ATMEGA164PA@MLF44 [CX4018]  
ATMEGA164PA@TQFP44 [CX3003]  
ATMEGA164PA@VFBGA49 [CX4018]  
ATMEGA164PV(ISP) [CX0001]  
ATMEGA164PV@MLF44(ISP) [CX0001]  
ATMEGA164PV@TQFP44(ISP) [CX0001]  
ATMEGA164V(ISP) [CX0001]  
ATMEGA164V@MLF44(ISP) [CX0001]  
ATMEGA164V@TQFP44(ISP) [CX0001]  
ATMEGA165@TQFP64 [CX3013]  
ATMEGA165A@TQFP64 [CX3044]  
ATMEGA165PA@TQFP64 [CX3044]  
ATMEGA165V@TQFP64 [CX3013]  
ATMEGA168(ISP) [CX0001]  
ATMEGA168@MLF32 [CX4015]  
ATMEGA168@MLP32(ISP) [CX0001]  
ATMEGA168@TQFP32(ISP) [CX0001]  
ATMEGA168A@MLF28 [CX4033]  
ATMEGA168A@TQFP32 [CX3001]  
ATMEGA168P(ISP) [CX0001]  
ATMEGA168P@MLF32 [CX4015]  
ATMEGA168P@MLP32(ISP) [CX0001]  
ATMEGA168P@TQFP32(ISP) [CX0001]  
ATMEGA168PA@MLF28 [CX4033]  
ATMEGA168PA@TQFP32 [CX3001]  
ATMEGA168PV(ISP) [CX0001]  
ATMEGA168PV@MLF32 [CX4015]  
ATMEGA168PV@MLP32(ISP) [CX0001]  
ATMEGA168PV@TQFP32(ISP) [CX0001]  
ATMEGA168V(ISP) [CX0001]  
ATMEGA168V@MLF32 [CX4015]  
ATMEGA168V@MLP32(ISP) [CX0001]  
ATMEGA168V@TQFP32(ISP) [CX0001]  
ATMEGA169@MLF64(ISP) [CX0001]  
ATMEGA169@TQFP64(ISP) [CX0001]  
ATMEGA169P@MLF64(ISP) [CX0001]  
ATMEGA169P@TQFP64(ISP) [CX0001]  
ATMEGA169PV@MLF64(ISP) [CX0001]  
ATMEGA169PV@TQFP64(ISP) [CX0001]  
ATMEGA169V@MLF64(ISP) [CX0001]  
ATMEGA169V@TQFP64(ISP) [CX0001]  
ATMEGA16A@MLF44 [CX4018]  
ATMEGA16HVA@TSOP28 [CX1024]  
ATMEGA16HVB@TSSOP44 [CX1012]  
ATMEGA16L@MLF44 [CX4018]  
ATMEGA16M1@MLF32 [CX4015]  
ATMEGA16M1@TQFP32 [CX3001]  
ATMEGA16U2@MLF32 [CX4015]  
ATMEGA16U4@MLF44 [CX4018]  
ATMEGA16U4@TQFP44 [CX3003]  
ATMEGA2560@CBGA100 [CX5055]  
ATMEGA2560@TQFP100 [CX3043]  
ATMEGA2560V@CBGA100 [CX5055]

ATMEGA2560V@TQFP100(ISP) [CX0001]  
ATMEGA2561@MLF64 [CX4023]  
ATMEGA2561@TQFP64 [CX3013]  
ATMEGA2561V@MLF64 [CX4023]  
ATMEGA2561V@TQFP64 [CX3013]  
ATMEGA256RFR2@QFN64 [CX4023]  
ATMEGA32@MLF44 [CX4018]  
ATMEGA323 [CX0001]  
ATMEGA323L [CX0001]  
ATMEGA324 [CX0001]  
ATMEGA324@MLF44 [CX4018]  
ATMEGA324@TQFP44 [CX3005]  
ATMEGA324A [CX0001]  
ATMEGA324A@MLF44 [CX4018]  
ATMEGA324A@TQFP44 [CX3003]  
ATMEGA324A@VFBGA49 [CX5154]  
ATMEGA324P [CX0001]  
ATMEGA324P@MLF44 [CX4018]  
ATMEGA324P@TQFP44 [CX3005]  
ATMEGA324PA [CX0001]  
ATMEGA324PA@MLF44 [CX4018]  
ATMEGA324PA@TQFP44 [CX3003]  
ATMEGA324PA@VFBGA49 [CX5154]  
ATMEGA324PA@VFBGA49(ISP) [CX0001]  
ATMEGA324PV [CX0001]  
ATMEGA324PV@MLF44 [CX4018]  
ATMEGA324PV@TQFP44 [CX3005]  
ATMEGA324V [CX0001]  
ATMEGA324V@MLF44 [CX4018]  
ATMEGA324V@TQFP44 [CX3005]  
ATMEGA325@MLF64 [CX4023]  
ATMEGA3250@TQFP100 [CX3043]  
ATMEGA3250PV@TQFP100 [CX3043]  
ATMEGA325P@MLF64 [CX4023]  
ATMEGA325PV@MLF64 [CX4023]  
ATMEGA325V@MLF64 [CX4023]  
ATMEGA328 [CX0001]  
ATMEGA328@MLF32 [CX4015]  
ATMEGA328P [CX0001]  
ATMEGA328P@MLF28 [CX4033]  
ATMEGA328P@MLP28(ISP) [CX0001]  
ATMEGA328P@TQFP32 [CX3001]  
ATMEGA328PV [CX0001]  
ATMEGA328PV@MLF28 [CX4033]  
ATMEGA328PV@MLP28(ISP) [CX0001]  
ATMEGA328PV@TQFP32 [CX3001]  
ATMEGA329@MLF64 [CX4023]  
ATMEGA3290@TQFP100 [CX3043]  
ATMEGA3290PV@TQFP100 [CX3043]  
ATMEGA329P@MLF64 [CX4023]  
ATMEGA329PV@MLF64 [CX4023]  
ATMEGA329V@MLF64 [CX4023]  
ATMEGA32A [CX0001]  
ATMEGA32A@TQFP44 [CX3005]  
ATMEGA32C1@MLF32(ISP) [CX0001]  
ATMEGA32C1@TQFP32(ISP) [CX0001]  
ATMEGA32L [CX0001]  
ATMEGA32L@TQFP44 [CX3005]  
ATMEGA32M1@MLF32(ISP) [CX0001]

ATMEGA2561@MLF64(ISP) [CX0001]  
ATMEGA2561@TQFP64(ISP) [CX0001]  
ATMEGA2561V@MLF64(ISP) [CX0001]  
ATMEGA2561V@TQFP64(ISP) [CX0001]  
ATMEGA32 [CX0001]  
ATMEGA32@TQFP44 [CX3005]  
ATMEGA323@TQFP44 [CX3002]  
ATMEGA323L@TQFP44 [CX3002]  
ATMEGA324(ISP) [CX0001]  
ATMEGA324@MLF44(ISP) [CX0001]  
ATMEGA324@TQFP44(ISP) [CX0001]  
ATMEGA324A(ISP) [CX0001]  
ATMEGA324A@MLF44(ISP) [CX0001]  
ATMEGA324A@TQFP44(ISP) [CX0001]  
ATMEGA324A@VFBGA49(ISP) [CX0001]  
ATMEGA324P(ISP) [CX0001]  
ATMEGA324P@MLF44(ISP) [CX0001]  
ATMEGA324P@TQFP44(ISP) [CX0001]  
ATMEGA324PA(ISP) [CX0001]  
ATMEGA324PA@MLF44(ISP) [CX0001]  
ATMEGA324PA@TQFP44(ISP) [CX0001]  
ATMEGA324PV(ISP) [CX0001]  
ATMEGA324PV@MLF44(ISP) [CX0001]  
ATMEGA324PV@TQFP44(ISP) [CX0001]  
ATMEGA324V(ISP) [CX0001]  
ATMEGA324V@MLF44(ISP) [CX0001]  
ATMEGA324V@TQFP44(ISP) [CX0001]  
ATMEGA325@TQFP64 [CX3013]  
ATMEGA3250P@TQFP100 [CX3043]  
ATMEGA3250V@TQFP100 [CX3043]  
ATMEGA325P@TQFP64 [CX3013]  
ATMEGA325PV@TQFP64 [CX3013]  
ATMEGA325V@TQFP64 [CX3013]  
ATMEGA328@MLF28 [CX4033]  
ATMEGA328@TQFP32 [CX3001]  
ATMEGA328P(ISP) [CX0001]  
ATMEGA328P@MLF32 [CX4015]  
ATMEGA328P@MLP32(ISP) [CX0001]  
ATMEGA328P@TQFP32(ISP) [CX0001]  
ATMEGA328PV(ISP) [CX0001]  
ATMEGA328PV@MLF32 [CX4015]  
ATMEGA328PV@MLP32(ISP) [CX0001]  
ATMEGA328PV@TQFP32(ISP) [CX0001]  
ATMEGA329@TQFP64 [CX3013]  
ATMEGA3290P@TQFP100 [CX3043]  
ATMEGA3290V@TQFP100 [CX3043]  
ATMEGA329P@TQFP64 [CX3013]  
ATMEGA329PV@TQFP64 [CX3013]  
ATMEGA329V@TQFP64 [CX3013]  
ATMEGA32A@MLF44 [CX4018]  
ATMEGA32C1@MLF32 [CX4015]  
ATMEGA32C1@TQFP32 [CX3001]  
ATMEGA32HVB@TSSOP44 [CX1012]  
ATMEGA32L@MLF44 [CX4018]  
ATMEGA32M1@MLF32 [CX4015]  
ATMEGA32M1@TQFP32 [CX3001]

ATMEGA32M1@TQFP32(ISP) [CX0001]  
ATMEGA32U2@VQFP32 [CX3001]  
ATMEGA32U4@MLF44(ISP) [CX0001]  
ATMEGA32U4@TQFP44(ISP) [CX0001]  
ATMEGA48 [CX0001]  
ATMEGA48@MLF28 [CX4033]  
ATMEGA48@MLP28(ISP) [CX0001]  
ATMEGA48@TQFP32 [CX3001]  
ATMEGA48A [CX0001]  
ATMEGA48A@MLF32 [CX4015]  
ATMEGA48P [CX0001]  
ATMEGA48P@MLF28 [CX4033]  
ATMEGA48P@MLP28(ISP) [CX0001]  
ATMEGA48P@TQFP32 [CX3001]  
ATMEGA48PA [CX0001]  
ATMEGA48PA@MLF32 [CX4015]  
ATMEGA48PV [CX0001]  
ATMEGA48PV@MLF28 [CX4033]  
ATMEGA48PV@MLP28(ISP) [CX0001]  
ATMEGA48PV@TQFP32 [CX3001]  
ATMEGA48V [CX0001]  
ATMEGA48V@MLF28 [CX4033]  
ATMEGA48V@MLP28(ISP) [CX0001]  
ATMEGA48V@TQFP32 [CX3001]  
ATMEGA603@TQFP64 [CX3013]  
ATMEGA64@MLF64 [CX4023]  
ATMEGA64@TQFP64 [CX3013]  
ATMEGA640@CBGA100 [CX5055]  
ATMEGA640@TQFP100 [CX3043]  
ATMEGA640V@CBGA100 [CX5055]  
ATMEGA640V@TQFP100 [CX3043]  
ATMEGA644 [CX0001]  
ATMEGA644@MLF44 [CX4018]  
ATMEGA644@TQFP44 [CX3005]  
ATMEGA644A [CX0001]  
ATMEGA644A@MLF44 [CX4018]  
ATMEGA644A@TQFP44 [CX3005]  
ATMEGA644P [CX0001]  
ATMEGA644P@MLF44 [CX4018]  
ATMEGA644P@TQFP44 [CX3005]  
ATMEGA644PA [CX0001]  
ATMEGA644PA@MLF44 [CX4018]  
ATMEGA644PA@TQFP44 [CX3005]  
ATMEGA644PV [CX0001]  
ATMEGA644PV@MLF44 [CX4018]  
ATMEGA644PV@TQFP44 [CX3005]  
ATMEGA644V [CX0001]  
ATMEGA644V@MLF44 [CX4018]  
ATMEGA644V@TQFP44 [CX3005]  
ATMEGA645@MLF64 [CX4023]  
ATMEGA6450@TQFP100 [CX3043]  
ATMEGA645V@MLF64 [CX4023]  
ATMEGA649@MLF64 [CX4023]  
ATMEGA6490@TQFP100 [CX3043]  
ATMEGA649V@MLF64 [CX4023]  
ATMEGA64A@MLF64 [CX4023]  
ATMEGA64C1@MLF32 [CX4015]  
ATMEGA64C1@TQFP32 [CX3001]  
ATMEGA64L@MLF64 [CX4023]  
ATMEGA32U2@MLF32 [CX4015]  
ATMEGA32U4@MLF44 [CX4018]  
ATMEGA32U4@TQFP44 [CX3003]  
ATMEGA406@LQFP48 [CX3007]  
ATMEGA48(ISP) [CX0001]  
ATMEGA48@MLF32 [CX4015]  
ATMEGA48@MLP32(ISP) [CX0001]  
ATMEGA48@TQFP32(ISP) [CX0001]  
ATMEGA48A@MLF28 [CX4033]  
ATMEGA48A@TQFP32 [CX3001]  
ATMEGA48P(ISP) [CX0001]  
ATMEGA48P@MLF32 [CX4015]  
ATMEGA48P@MLP32(ISP) [CX0001]  
ATMEGA48P@TQFP32(ISP) [CX0001]  
ATMEGA48PA@MLF28 [CX4033]  
ATMEGA48PA@TQFP32 [CX3001]  
ATMEGA48PV(ISP) [CX0001]  
ATMEGA48PV@MLF32 [CX4015]  
ATMEGA48PV@MLP32(ISP) [CX0001]  
ATMEGA48PV@TQFP32(ISP) [CX0001]  
ATMEGA48V(ISP) [CX0001]  
ATMEGA48V@MLF32 [CX4015]  
ATMEGA48V@MLP32(ISP) [CX0001]  
ATMEGA48V@TQFP32(ISP) [CX0001]  
ATMEGA603L@TQFP64 [CX3013]  
ATMEGA64@MLF64(ISP) [CX0001]  
ATMEGA64@TQFP64(ISP) [CX0001]  
ATMEGA640@CBGA100(ISP) [CX0001]  
ATMEGA640@TQFP100(ISP) [CX0001]  
ATMEGA640V@CBGA100(ISP) [CX0001]  
ATMEGA640V@TQFP100(ISP) [CX0001]  
ATMEGA644(ISP) [CX0001]  
ATMEGA644@MLF44(ISP) [CX0001]  
ATMEGA644@TQFP44(ISP) [CX0001]  
ATMEGA644A(ISP) [CX0001]  
ATMEGA644A@MLF44(ISP) [CX0001]  
ATMEGA644A@TQFP44(ISP) [CX0001]  
ATMEGA644P(ISP) [CX0001]  
ATMEGA644P@MLF44(ISP) [CX0001]  
ATMEGA644P@TQFP44(ISP) [CX0001]  
ATMEGA644PA(ISP) [CX0001]  
ATMEGA644PA@MLF44(ISP) [CX0001]  
ATMEGA644PA@TQFP44(ISP) [CX0001]  
ATMEGA644PV(ISP) [CX0001]  
ATMEGA644PV@MLF44(ISP) [CX0001]  
ATMEGA644PV@TQFP44(ISP) [CX0001]  
ATMEGA644V(ISP) [CX0001]  
ATMEGA644V@MLF44(ISP) [CX0001]  
ATMEGA644V@TQFP44(ISP) [CX0001]  
ATMEGA645@TQFP64 [CX3013]  
ATMEGA6450V@TQFP100 [CX3043]  
ATMEGA645V@TQFP64 [CX3013]  
ATMEGA649@TQFP64 [CX3013]  
ATMEGA6490V@TQFP100 [CX3043]  
ATMEGA649V@TQFP64 [CX3013]  
ATMEGA64A@TQFP64 [CX3013]  
ATMEGA64C1@MLF32(ISP) [CX0001]  
ATMEGA64C1@TQFP32(ISP) [CX0001]  
ATMEGA64L@MLF64(ISP) [CX0001]

ATMEGA64L@TQFP64 [CX3013]  
ATMEGA64M1@MLF32 [CX4015]  
ATMEGA64M1@TQFP32 [CX3001]  
ATMEGA64RFR2@QFN64 [CX4023]  
ATMEGA8(ISP) [CX0001]  
ATMEGA8@MLF32(ISP) [CX0001]  
ATMEGA8@TQFP32(ISP) [CX0001]  
ATMEGA8515@MLF44 [CX4018]  
ATMEGA8515@TQFP44 [CX3005]  
ATMEGA8515L@MLF44 [CX4018]  
ATMEGA8515L@TQFP44 [CX3005]  
ATMEGA8535(ISP) [CX0001]  
ATMEGA8535@MLF44(ISP) [CX0001]  
ATMEGA8535@PLCC44(ISP) [CX0001]  
ATMEGA8535@TQFP44(ISP) [CX0001]  
ATMEGA8535L(ISP) [CX0001]  
ATMEGA8535L@MLF44(ISP) [CX0001]  
ATMEGA8535L@PLCC44(ISP) [CX0001]  
ATMEGA8535L@TQFP44(ISP) [CX0001]  
ATMEGA88(ISP) [CX0001]  
ATMEGA88@MLF32 [CX4015]  
ATMEGA88@MLP32(ISP) [CX0001]  
ATMEGA88@TQFP32(ISP) [CX0001]  
ATMEGA88A@MLF28 [CX4033]  
ATMEGA88A@TQFP32 [CX3001]  
ATMEGA88P(ISP) [CX0001]  
ATMEGA88P@MLF32 [CX4015]  
ATMEGA88P@MLP32(ISP) [CX0001]  
ATMEGA88P@TQFP32(ISP) [CX0001]  
ATMEGA88PA@MLF28 [CX4033]  
ATMEGA88PA@TQFP32 [CX3001]  
ATMEGA88PV(ISP) [CX0001]  
ATMEGA88PV@MLF32 [CX4015]  
ATMEGA88PV@MLP32(ISP) [CX0001]  
ATMEGA88PV@TQFP32(ISP) [CX0001]  
ATMEGA88V(ISP) [CX0001]  
ATMEGA88V@MLF32 [CX4015]  
ATMEGA88V@MLP32(ISP) [CX0001]  
ATMEGA88V@TQFP32(ISP) [CX0001]  
ATMEGA8A@MLF32 [CX4015]  
ATMEGA8HVA@TSOP28 [CX1024]  
ATMEGA8L [CX0001]  
ATMEGA8L@MLF32 [CX4015]  
ATMEGA8L@TQFP32 [CX3001]  
ATMEGA8U2@MLF32 [CX4015]  
ATSAM3N00A@LQFP48 [CX3007]  
ATSAM3N00B@LQFP64 [CX3011]  
ATSAM3N0A@LQFP48 [CX3007]  
ATSAM3N0B@LQFP64 [CX3011]  
ATSAM3N0C@BGA100 [CX5055]  
ATSAM3N1A@LQFP48 [CX3007]  
ATSAM3N1B@LQFP64 [CX3011]  
ATSAM3N1C@BGA100 [CX5055]  
ATSAM3N2A@LQFP48 [CX3007]  
ATSAM3N2B@LQFP64 [CX3011]  
ATSAM3N2C@BGA100 [CX5055]  
ATSAM3N4A@LQFP48 [CX3007]  
ATSAM3N4B@LQFP64 [CX3011]  
ATSAM3N4C@BGA100 [CX5055]  
ATMEGA64L@TQFP64(ISP) [CX0001]  
ATMEGA64M1@MLF32(ISP) [CX0001]  
ATMEGA64M1@TQFP32(ISP) [CX0001]  
ATMEGA8 [CX0001]  
ATMEGA8@MLF32 [CX4015]  
ATMEGA8@TQFP32 [CX3001]  
ATMEGA8515 [CX0001]  
ATMEGA8515@PLCC44 [CX2044]  
ATMEGA8515L [CX0001]  
ATMEGA8515L@PLCC44 [CX2044]  
ATMEGA8535 [CX0001]  
ATMEGA8535@MLF44 [CX4018]  
ATMEGA8535@PLCC44 [CX2044]  
ATMEGA8535@TQFP44 [CX3005]  
ATMEGA8535L [CX0001]  
ATMEGA8535L@MLF44 [CX4018]  
ATMEGA8535L@PLCC44 [CX2044]  
ATMEGA8535L@TQFP44 [CX3005]  
ATMEGA88 [CX0001]  
ATMEGA88@MLF28 [CX4033]  
ATMEGA88@MLP28(ISP) [CX0001]  
ATMEGA88@TQFP32 [CX3001]  
ATMEGA88A [CX0001]  
ATMEGA88A@MLF32 [CX4015]  
ATMEGA88P [CX0001]  
ATMEGA88P@MLF28 [CX4033]  
ATMEGA88P@MLP28(ISP) [CX0001]  
ATMEGA88P@TQFP32 [CX3001]  
ATMEGA88PA [CX0001]  
ATMEGA88PA@MLF32 [CX4015]  
ATMEGA88PV [CX0001]  
ATMEGA88PV@MLF28 [CX4033]  
ATMEGA88PV@MLP28(ISP) [CX0001]  
ATMEGA88PV@TQFP32 [CX3001]  
ATMEGA88V [CX0001]  
ATMEGA88V@MLF28 [CX4033]  
ATMEGA88V@MLP28(ISP) [CX0001]  
ATMEGA88V@TQFP32 [CX3001]  
ATMEGA8A [CX0001]  
ATMEGA8A@TQFP32 [CX3001]  
ATMEGA8HVA@TSOP28(ISP) [CX0001]  
ATMEGA8L(ISP) [CX0001]  
ATMEGA8L@MLF32(ISP) [CX0001]  
ATMEGA8L@TQFP32(ISP) [CX0001]  
ATMEGA8U2@VQFP32 [CX3001]  
ATSAM3N00A@QFN48 [CX4021]  
ATSAM3N00B@QFN64 [CX4023]  
ATSAM3N0A@QFN48 [CX4021]  
ATSAM3N0B@QFN64 [CX4023]  
ATSAM3N0C@LBFP100 [CX3043]  
ATSAM3N1A@QFN48 [CX4021]  
ATSAM3N1B@QFN64 [CX4023]  
ATSAM3N1C@LBFP100 [CX3043]  
ATSAM3N2A@QFN48 [CX4021]  
ATSAM3N2B@QFN64 [CX4023]  
ATSAM3N2C@LBFP100 [CX3043]  
ATSAM3N4A@QFN48 [CX4021]  
ATSAM3N4B@QFN64 [CX4023]  
ATSAM3N4C@LBFP100 [CX3043]

ATSAM3S1A@LQFP48 [CX3007]                    ATSAM3S1A@QFN48 [CX4021]  
ATSAM3S1B@LQFP64 [CX3011]                    ATSAM3S1B@QFN64 [CX4023]  
ATSAM3S1C@BGA100 [CX5055]                    ATSAM3S1C@LQFP100 [CX3043]  
ATSAM3S2A@LQFP48 [CX3007]                    ATSAM3S2A@QFN48 [CX4021]  
ATSAM3S2B@LQFP64 [CX3011]                    ATSAM3S2B@QFN64 [CX4023]  
ATSAM3S2C@BGA100 [CX5055]                    ATSAM3S2C@LQFP100 [CX3043]  
ATSAM3S4A@LQFP48 [CX3007]                    ATSAM3S4A@QFN48 [CX4021]  
ATSAM3S4B@QFN64 [CX4023]                    ATSAM3S4B@QFP64 [CX3011]  
ATSAM3S4C@BGA100 [CX5055]                    ATSAM3S4C@QFP100 [CX3043]  
ATSAM3U1C@FBGA100 [CX5055]                    ATSAM3U1C@LQFP100 [CX3043]  
ATSAM3U2C@FBGA100 [CX5055]                    ATSAM3U2C@LQFP100 [CX3043]  
ATSAM3U4C@FBGA100 [CX5055]                    ATSAM3U4C@LQFP100 [CX3043]  
ATSAM3X4C@LQFP100 [CX3043]                    ATSAM3X8C@LQFP100 [CX3043]  
ATSHA204-MAH-CZ@QFN8 [CX4002]                    ATSHA204-MAH-DA@QFN8 [CX4002]  
ATSHA204-SH-CZ@SOIC8 [CX1045]                    ATSHA204-SH-DA@SOIC8 [CX1045]  
ATSHA204-TH-CZ@TSSOP8 [CX1000]                    ATSHA204-TH-DA@TSSOP8 [CX1000]  
ATtiny10 [CX0001]                    ATtiny10(ISP) [CX0001]  
ATtiny10@SOIC8 [CX1031]                    ATtiny10@SOIC8(ISP) [CX0001]  
ATtiny10@SOT23 [CX1041]                    ATtiny10@SOT23(ISP) [CX0001]  
ATtiny11 [CX0001]                    ATtiny11(ISP) [CX0001]  
ATtiny11@SOIC8 [CX1031]                    ATtiny11@SOIC8(ISP) [CX0001]  
ATtiny11L [CX0001]                    ATtiny11L(ISP) [CX0001]  
ATtiny11L@SOIC8 [CX1031]                    ATtiny11L@SOIC8(ISP) [CX0001]  
ATtiny12 [CX0001]                    ATtiny12(ISP) [CX0001]  
ATtiny12@SOIC8 [CX1031]                    ATtiny12@SOIC8(ISP) [CX0001]  
ATtiny12L [CX0001]                    ATtiny12L(ISP) [CX0001]  
ATtiny12L@SOIC8 [CX1031]                    ATtiny12L@SOIC8(ISP) [CX0001]  
ATtiny12V [CX0001]                    ATtiny12V(ISP) [CX0001]  
ATtiny12V@SOIC8 [CX1031]                    ATtiny12V@SOIC8(ISP) [CX0001]  
ATtiny13 [CX0001]                    ATtiny13(ISP) [CX0001]  
ATtiny13@MLF10 [CX4007]                    ATtiny13@MLF10(ISP) [CX0001]  
ATtiny13@MLF20 [CX4011]                    ATtiny13@MLF20(ISP) [CX0001]  
ATtiny13@SOIC8(3.9\*6.2) [CX1016]                     
ATtiny13@SOIC8(3.9\*6.2)(ISP) [CX0001]                     
ATtiny13@SOIC8(5.5\*8.0) [CX1031]                     
ATtiny13@SOIC8(5.5\*8.0)(ISP) [CX0001]                     
ATtiny13A [CX0001]                    ATtiny13A@MLF10 [CX4007]  
ATtiny13A@MLF20 [CX4011]                     
ATtiny13A@SOIC8(3.9\*6.2) [CX1016]                     
ATtiny13A@SOIC8(5.5\*8.0) [CX1031]                     
ATtiny13V [CX0001]                    ATtiny13V(ISP) [CX0001]  
ATtiny13V@MLF10 [CX4007]                    ATtiny13V@MLF10(ISP) [CX0001]  
ATtiny13V@MLF20 [CX4011]                    ATtiny13V@MLF20(ISP) [CX0001]  
ATtiny13V@SOIC8(3.9\*6.2) [CX1016]                     
ATtiny13V@SOIC8(3.9\*6.2)(ISP) [CX0001]                     
ATtiny13V@SOIC8(5.5\*8.0) [CX1031]                     
ATtiny13V@SOIC8(5.5\*8.0)(ISP) [CX0001]                     
ATtiny15 [CX0001]                    ATtiny15(ISP) [CX0001]  
ATtiny15@SOIC8 [CX1031]                    ATtiny15@SOIC8(ISP) [CX0001]  
ATtiny15L [CX0001]                    ATtiny15L(ISP) [CX0001]  
ATtiny15L@SOIC8 [CX1031]                    ATtiny15L@SOIC8(ISP) [CX0001]  
ATtiny1634@QFN20 [CX4011]                    ATtiny1634@SOIC20 [CX1033]  
ATtiny167@QFN32 [CX4015]                    ATtiny167@QFN32(ISP) [CX0001]  
ATtiny167@SOIC20 [CX1033]                    ATtiny167@SOIC20(ISP) [CX0001]  
ATtiny167@TSSOP20 [CX1000]                    ATtiny167@TSSOP20(ISP) [CX0001]  
ATtiny20@QFN20 [CX4044]                    ATtiny20@SOIC14 [CX1016]  
ATtiny20@TSSOP14 [CX1000]                    ATtiny2313 [CX0001]  
ATtiny2313(ISP) [CX0001]                    ATtiny2313@MLF20 [CX4011]  
ATtiny2313@QFN20(ISP) [CX0001]                    ATtiny2313@SOIC20 [CX1033]

ATtiny2313@SOIC20(ISP) [CX0001]      ATtiny2313AMMH@MLF20 [CX4011]  
ATtiny2313AMU@MLF20 [CX4011]      ATtiny2313APU [CX0001]  
ATtiny2313ASU@SOIC20 [CX1033]      ATtiny2313V [CX0001]  
ATtiny2313V(ISP) [CX0001]      ATtiny2313V@MLF20 [CX4011]  
ATtiny2313V@QFN20(ISP) [CX0001]      ATtiny2313V@SOIC20 [CX1033]  
ATtiny2313V@SOIC20(ISP) [CX0001]      ATtiny24 [CX0001]  
ATtiny24(ISP) [CX0001]      ATtiny24(low vol isp) [CX0001]  
ATtiny24@MLF20 [CX4011]      ATtiny24@MLF20(ISP) [CX0001]  
ATtiny24@MLF20(low vol isp) [CX0001]  
ATtiny24@SOIC14 [CX1016]      ATtiny24@SOIC14(ISP) [CX0001]  
ATtiny24@SOIC14(low vol isp) [CX0001]  
ATtiny24A [CX0001]      ATtiny24A@MLF20(3\*3) [CX4044]  
ATtiny24A@MLF20(4\*4) [CX4011]      ATtiny24A@SOIC14 [CX1016]  
ATtiny24V [CX0001]      ATtiny24V(ISP) [CX0001]  
ATtiny24V(low vol isp) [CX0001]      ATtiny24V@MLF20 [CX4011]  
ATtiny24V@MLF20(ISP) [CX0001]  
ATtiny24V@MLF20(low vol isp) [CX0001]  
ATtiny24V@SOIC14 [CX1016]      ATtiny24V@SOIC14(ISP) [CX0001]  
ATtiny24V@SOIC14(low vol isp) [CX0001]  
ATtiny25 [CX0001]      ATtiny25(ISP) [CX0001]  
ATtiny25(low vol isp) [CX0001]      ATtiny25@MLF20 [CX4011]  
ATtiny25@MLF20(ISP) [CX0001]  
ATtiny25@MLF20(low vol isp) [CX0001]  
ATtiny25@SOIC8 [CX1031]      ATtiny25@SOIC8(ISP) [CX0001]  
ATtiny25@SOIC8(low vol isp) [CX0001]  
ATtiny25V [CX0001]      ATtiny25V(ISP) [CX0001]  
ATtiny25V(low vol isp) [CX0001]      ATtiny25V@MLF20 [CX4011]  
ATtiny25V@MLF20(ISP) [CX0001]  
ATtiny25V@MLF20(low vol isp) [CX0001]  
ATtiny25V@SOIC8 [CX1031]      ATtiny25V@SOIC8(ISP) [CX0001]  
ATtiny25V@SOIC8(low vol isp) [CX0001]  
ATtiny26 [CX0001]      ATtiny26(ISP) [CX0001]  
ATtiny26(new) [CX0001]      ATtiny26(new)(ISP) [CX0001]  
ATtiny26(new)@MLF32 [CX4015]      ATtiny26(new)@SOIC20 [CX1033]  
ATtiny26(new)@SOIC20(ISP) [CX0001]  
ATtiny26(new)@TSSOP20 [CX1000]  
ATtiny26(new)@TSSOP20(ISP) [CX0001]  
ATtiny26@MLF32 [CX4015]      ATtiny26@MLF32(ISP) [CX0001]  
ATtiny26@SOIC20 [CX1033]      ATtiny26@SOIC20(ISP) [CX0001]  
ATtiny26@TSSOP20 [CX1000]      ATtiny26@TSSOP20(ISP) [CX0001]  
ATtiny261 [CX0001]      ATtiny261(ISP) [CX0001]  
ATtiny261@MLF32 [CX4015]      ATtiny261@MLF32(ISP) [CX0001]  
ATtiny261@SOIC20 [CX1033]      ATtiny261@SOIC20(ISP) [CX0001]  
ATtiny261@TSSOP20 [CX1000]      ATtiny261A [CX0001]  
ATtiny261A(ISP) [CX0001]      ATtiny261A@MLF32 [CX4015]  
ATtiny261A@MLF32(ISP) [CX0001]      ATtiny261A@SOIC20 [CX1033]  
ATtiny261A@SOIC20(ISP) [CX0001]      ATtiny261A@TSSOP20 [CX1000]  
ATtiny261V [CX0001]      ATtiny261V(ISP) [CX0001]  
ATtiny261V@MLF32 [CX4015]      ATtiny261V@MLF32(ISP) [CX0001]  
ATtiny261V@SOIC20 [CX1033]      ATtiny261V@SOIC20(ISP) [CX0001]  
ATtiny261V@TSSOP20 [CX1000]      ATtiny26L [CX0001]  
ATtiny26L(ISP) [CX0001]      ATtiny26L(new) [CX0001]  
ATtiny26L(new)(ISP) [CX0001]      ATtiny26L(new)@MLF32 [CX4015]  
ATtiny26L(new)@SOIC20 [CX1033]  
ATtiny26L(new)@SOIC20(ISP) [CX0001]  
ATtiny26L(new)@TSSOP20 [CX1000]  
ATtiny26L(new)@TSSOP20(ISP) [CX0001]  
ATtiny26L@MLF32 [CX4015]      ATtiny26L@MLF32(ISP) [CX0001]  
ATtiny26L@SOIC20 [CX1033]      ATtiny26L@SOIC20(ISP) [CX0001]

ATtiny26L@TSSOP20 [CX1000]                    ATtiny26L@TSSOP20(ISP) [CX0001]  
ATtiny26LN@MLF32(ISP) [CX0001]            ATtiny26N@MLF32(ISP) [CX0001]  
ATtiny28L [CX0001]                            ATtiny28L@MLF32 [CX4015]  
ATtiny28L@TQFP32 [CX3001]                   ATtiny28V [CX0001]  
ATtiny28V@MLF32 [CX4015]                    ATtiny28V@TQFP32 [CX3001]  
ATtiny4@SOT23 [CX1041]                      ATtiny40@QFN20 [CX4044]  
ATtiny40@SOIC20 [CX1033]                    ATtiny40@TSSOP20 [CX1000]  
ATtiny4313MMH@MLF20 [CX50UN]                ATtiny4313MU@MLF20 [CX4011]  
ATtiny4313PU [CX0001]                        ATtiny4313SU@SOIC20 [CX1033]  
ATtiny43U@MLF20 [CX4011]                    ATtiny43U@SOIC20 [CX1033]  
ATtiny44 [CX0001]                            ATtiny44(ISP) [CX0001]  
ATtiny44(low vol isp) [CX0001]              ATtiny44@MLF20 [CX4011]  
ATtiny44@MLF20(ISP) [CX0001]  
ATtiny44@MLF20(low vol isp) [CX0001]  
ATtiny44@SOIC14 [CX1016]                    ATtiny44@SOIC14(ISP) [CX0001]  
ATtiny44@SOIC14(low vol isp) [CX0001]  
ATtiny44A [CX0001]                            ATtiny44A@MLF20(3\*3) [CX4044]  
ATtiny44A@MLF20(4\*4) [CX4011]              ATtiny44A@SOIC14 [CX1016]  
ATtiny44V [CX0001]                            ATtiny44V(ISP) [CX0001]  
ATtiny44V(low vol isp) [CX0001]              ATtiny44V@MLF20 [CX4011]  
ATtiny44V@MLF20(ISP) [CX0001]  
ATtiny44V@MLF20(low vol isp) [CX0001]  
ATtiny44V@SOIC14 [CX1016]                   ATtiny44V@SOIC14(ISP) [CX0001]  
ATtiny44V@SOIC14(low vol isp) [CX0001]  
ATtiny45 [CX0001]                            ATtiny45(ISP) [CX0001]  
ATtiny45(low vol isp) [CX0001]              ATtiny45@MLF20 [CX4011]  
ATtiny45@MLF20(ISP) [CX0001]  
ATtiny45@MLF20(low vol isp) [CX0001]  
ATtiny45@SOIC8 [CX1031]                      ATtiny45@SOIC8(ISP) [CX0001]  
ATtiny45@SOIC8(low vol isp) [CX0001]  
ATtiny45V [CX0001]                            ATtiny45V(ISP) [CX0001]  
ATtiny45V(low vol isp) [CX0001]              ATtiny45V@MLF20 [CX4011]  
ATtiny45V@MLF20(ISP) [CX0001]  
ATtiny45V@MLF20(low vol isp) [CX0001]  
ATtiny45V@SOIC8 [CX1031]                    ATtiny45V@SOIC8(ISP) [CX0001]  
ATtiny45V@SOIC8(low vol isp) [CX0001]  
ATtiny461 [CX0001]                            ATtiny461(ISP) [CX0001]  
ATtiny461@MLF32 [CX4015]                    ATtiny461@MLF32(ISP) [CX0001]  
ATtiny461@SOIC20 [CX1033]                    ATtiny461@SOIC20(ISP) [CX0001]  
ATtiny461@TSSOP20 [CX1000]                  ATtiny461A [CX0001]  
ATtiny461A(ISP) [CX0001]                    ATtiny461A@MLF32 [CX4015]  
ATtiny461A@MLF32(ISP) [CX0001]            ATtiny461A@SOIC20 [CX1033]  
ATtiny461A@SOIC20(ISP) [CX0001]            ATtiny461A@TSSOP20 [CX1000]  
ATtiny461V [CX0001]                            ATtiny461V(ISP) [CX0001]  
ATtiny461V@MLF32 [CX4015]                    ATtiny461V@MLF32(ISP) [CX0001]  
ATtiny461V@SOIC20 [CX1033]                   ATtiny461V@SOIC20(ISP) [CX0001]  
ATtiny461V@TSSOP20 [CX1000]                  ATtiny48 [CX0001]  
ATtiny48(ISP) [CX0001]                        ATtiny48@MLF28 [CX4033]  
ATtiny48@MLF28(ISP) [CX0001]                ATtiny48@MLF32 [CX4015]  
ATtiny48@MLF32(ISP) [CX0001]                ATtiny48@TQFP32 [CX3001]  
ATtiny48@TQFP32(ISP) [CX0001]                ATtiny48V [CX0001]  
ATtiny48V(ISP) [CX0001]                        ATtiny48V@MLF28 [CX4033]  
ATtiny48V@MLF28(ISP) [CX0001]                ATtiny48V@MLF32 [CX4015]  
ATtiny48V@MLF32(ISP) [CX0001]                ATtiny48V@TQFP32 [CX3001]  
ATtiny48V@TQFP32(ISP) [CX0001]                ATtiny5@SOT23 [CX1041]  
ATtiny828@MLF32 [CX4015]                    ATtiny828@TQFP32 [CX3001]  
ATtiny84 [CX0001]                            ATtiny84(ISP) [CX0001]  
ATtiny84(low vol isp) [CX0001]                ATtiny84@MLF20 [CX4011]  
ATtiny84@MLF20(ISP) [CX0001]

ATtiny84@MLF20(low vol isp) [CX0001]  
ATtiny84@SOIC14 [CX1016] ATtiny84@SOIC14(ISP) [CX0001]  
ATtiny84@SOIC14(low vol isp) [CX0001]  
ATtiny84A [CX0001] ATtiny84A@MLF20(3\*3) [CX4044]  
ATtiny84A@MLF20(4\*4) [CX4011] ATtiny84A@SOIC14 [CX1016]  
ATtiny84V [CX0001] ATtiny84V(ISP) [CX0001]  
ATtiny84V(low vol isp) [CX0001] ATtiny84V@MLF20 [CX4011]  
ATtiny84V@MLF20(ISP) [CX0001]  
ATtiny84V@MLF20(low vol isp) [CX0001]  
ATtiny84V@SOIC14 [CX1016] ATtiny84V@SOIC14(ISP) [CX0001]  
ATtiny84V@SOIC14(low vol isp) [CX0001]  
ATtiny85 [CX0001] ATtiny85(ISP) [CX0001]  
ATtiny85(low vol isp) [CX0001] ATtiny85@MLF20 [CX4011]  
ATtiny85@MLF20(ISP) [CX0001]  
ATtiny85@MLF20(low vol isp) [CX0001]  
ATtiny85@SOIC8 [CX1031] ATtiny85@SOIC8(ISP) [CX0001]  
ATtiny85@SOIC8(low vol isp) [CX0001]  
ATtiny85V [CX0001] ATtiny85V(ISP) [CX0001]  
ATtiny85V(low vol isp) [CX0001] ATtiny85V@MLF20 [CX4011]  
ATtiny85V@MLF20(ISP) [CX0001]  
ATtiny85V@MLF20(low vol isp) [CX0001]  
ATtiny85V@SOIC8 [CX1031] ATtiny85V@SOIC8(ISP) [CX0001]  
ATtiny85V@SOIC8(low vol isp) [CX0001]  
ATtiny861 [CX0001] ATtiny861(ISP) [CX0001]  
ATtiny861@MLF32 [CX4015] ATtiny861@MLF32(ISP) [CX0001]  
ATtiny861@SOIC20 [CX1033] ATtiny861@SOIC20(ISP) [CX0001]  
ATtiny861@TSSOP20 [CX1000] ATtiny861A [CX0001]  
ATtiny861A(ISP) [CX0001] ATtiny861A@MLF32 [CX4015]  
ATtiny861A@MLF32(ISP) [CX0001] ATtiny861A@SOIC20 [CX1033]  
ATtiny861A@SOIC20(ISP) [CX0001] ATtiny861A@TSSOP20 [CX1000]  
ATtiny861V [CX0001] ATtiny861V(ISP) [CX0001]  
ATtiny861V@MLF32 [CX4015] ATtiny861V@MLF32(ISP) [CX0001]  
ATtiny861V@SOIC20 [CX1033] ATtiny861V@SOIC20(ISP) [CX0001]  
ATtiny861V@TSSOP20 [CX1000] ATtiny87@QFN32 [CX4015]  
ATtiny87@QFN32(ISP) [CX0001] ATtiny87@SOIC20 [CX1033]  
ATtiny87@SOIC20(ISP) [CX0001] ATtiny87@TSSOP20 [CX1000]  
ATtiny87@TSSOP20(ISP) [CX0001] ATtiny88 [CX0001]  
ATtiny88(ISP) [CX0001] ATtiny88@MLF28 [CX4033]  
ATtiny88@MLF28(ISP) [CX0001] ATtiny88@MLF32 [CX4015]  
ATtiny88@MLF32(ISP) [CX0001] ATtiny88@TQFP32 [CX3001]  
ATtiny88@TQFP32(ISP) [CX0001] ATtiny88V [CX0001]  
ATtiny88V(ISP) [CX0001] ATtiny88V@MLF28 [CX4033]  
ATtiny88V@MLF28(ISP) [CX0001] ATtiny88V@MLF32 [CX4015]  
ATtiny88V@MLF32(ISP) [CX0001] ATtiny88V@TQFP32 [CX3001]  
ATtiny88V@TQFP32(ISP) [CX0001] ATtiny9@SOT23 [CX1041]  
ATUC128D3@QFN64 [CX4023] ATUC128D3@QFP64 [CX3011]  
ATUC128D4@QFN48 [CX4021] ATUC128D4@QFP48 [CX3007]  
ATUC128L3U@QFN64 [CX4023] ATUC128L3U@TQFP64 [CX3011]  
ATUC128L4U@QFN48 [CX4021] ATUC128L4U@TQFP48 [CX3007]  
ATUC256L3U@QFN64 [CX4023] ATUC256L3U@TQFP64 [CX3011]  
ATUC256L4U@QFN48 [CX4021] ATUC256L4U@TQFP48 [CX3007]  
ATUC64D3@QFN64 [CX4023] ATUC64D3@QFP64 [CX3011]  
ATUC64D4@QFN48 [CX4021] ATUC64D4@QFP48 [CX3007]  
ATUC64L3U@QFN64 [CX4023] ATUC64L3U@TQFP64 [CX3011]  
ATUC64L4U@QFN48 [CX4021] ATUC64L4U@TQFP48 [CX3007]  
ATxmega128A1@BGA100 [CX5055] ATxmega128A1@TQFP100 [CX3043]  
ATxmega128A1U@CBGA100 [CX5055] ATxmega128A1U@TQFP100 [CX3043]  
ATxmega128A1U@VFBGA100 [CX5215] ATxmega128A3@QFN64 [CX4023]  
ATxmega128A3@TQFP64 [CX3044] ATxmega128A3U@QFN64 [CX4023]



ATxmega128A3U@TQFP64 [CX3044]  
ATxmega128A4@TQFP44 [CX3005]  
ATxmega128A4U@QFN44 [CX4018]  
ATxmega128B1@TQFP100 [CX3043]  
ATxmega128B3@TQFP64 [CX3044]  
ATxmega128C3@TQFP64 [CX3044]  
ATxmega128D3@TQFP64 [CX3044]  
ATxmega128D4@TQFP44 [CX3005]  
ATxmega16A4@TQFP44 [CX3005]  
ATxmega16A4U@BGA49 [CX5154]  
ATxmega16A4U@TQFP44 [CX3005]  
ATxmega16C4@TQFP44 [CX3005]  
ATxmega16D4@QFN44 [CX4018]  
ATxmega16D4@VFBGA49 [CX5154]  
ATxmega16E5@UQFN32 [CX4084]  
ATxmega192A1@BGA100 [CX5055]  
ATxmega192A3@QFN64 [CX4023]  
ATxmega192A3U@QFN64 [CX4023]  
ATxmega192C3@QFN64 [CX4023]  
ATxmega192D3@QFN64 [CX4023]  
ATxmega256A1@BGA100 [CX5055]  
ATxmega256A3@QFN64 [CX4023]  
ATxmega256A3B@QFN64 [CX4023]  
ATxmega256A3BU@QFN64 [CX4023]  
ATxmega256A3U@QFN64 [CX4023]  
ATxmega256C3@QFN64 [CX4023]  
ATxmega256D3@QFN64 [CX4023]  
ATxmega32A4@QFN44 [CX4018]  
ATxmega32A4@VFBGA49 [CX5154]  
ATxmega32A4U@QFN44 [CX4018]  
ATxmega32C4@QFN44 [CX4018]  
ATxmega32C4@VFBGA49 [CX5154]  
ATxmega32D4@TQFP44 [CX3005]  
ATxmega32E5@TQFP32 [CX3001]  
ATxmega32E5@VQFN32 [CX4015]  
ATxmega384C3@TQFP64 [CX3044]  
ATxmega64A1@TQFP100 [CX3043]  
ATxmega64A1U@TQFP100 [CX3043]  
ATxmega64A3@QFN64 [CX4023]  
ATxmega64A3U@QFN64 [CX4023]  
ATxmega64A4@QFN44 [CX4018]  
ATxmega64A4U@BGA49 [CX5154]  
ATxmega64A4U@TQFP44 [CX3005]  
ATxmega64B3@QFN64 [CX4023]  
ATxmega64C3@QFN64 [CX4023]  
ATxmega64D3@QFN64 [CX4023]  
ATxmega64D4@QFN44 [CX4018]  
ATxmega8E5@TQFP32 [CX3001]  
ATxmega8E5@VQFN32 [CX4015]  
T89F64 [CX0001]  
T89F64@TQFP44 [CX3003]  
ATxmega128A4@QFN44 [CX4018]  
ATxmega128A4U@BGA49 [CX5154]  
ATxmega128A4U@TQFP44 [CX3005]  
ATxmega128B3@QFN64 [CX4023]  
ATxmega128C3@QFN64 [CX4023]  
ATxmega128D3@QFN64 [CX4023]  
ATxmega128D4@QFN44 [CX4018]  
ATxmega16A4@QFN44 [CX4018]  
ATxmega16A4@VFBGA49 [CX5154]  
ATxmega16A4U@QFN44 [CX4018]  
ATxmega16C4@QFN44 [CX4018]  
ATxmega16C4@VFBGA49 [CX5154]  
ATxmega16D4@TQFP44 [CX3005]  
ATxmega16E5@TQFP32 [CX3001]  
ATxmega16E5@VQFN32 [CX4015]  
ATxmega192A1@TQFP100 [CX3043]  
ATxmega192A3@TQFP64 [CX3044]  
ATxmega192A3U@TQFP64 [CX3044]  
ATxmega192C3@TQFP64 [CX3044]  
ATxmega192D3@TQFP64 [CX3044]  
ATxmega256A1@TQFP100 [CX3043]  
ATxmega256A3@TQFP64 [CX3044]  
ATxmega256A3B@TQFP64 [CX3044]  
ATxmega256A3BU@TQFP64 [CX3044]  
ATxmega256A3U@TQFP64 [CX3044]  
ATxmega256C3@TQFP64 [CX3044]  
ATxmega256D3@TQFP64 [CX3044]  
ATxmega32A4@TQFP44 [CX3005]  
ATxmega32A4U@BGA49 [CX5154]  
ATxmega32A4U@TQFP44 [CX3005]  
ATxmega32C4@TQFP44 [CX3005]  
ATxmega32D4@QFN44 [CX4018]  
ATxmega32D4@VFBGA49 [CX5154]  
ATxmega32E5@UQFN32 [CX4084]  
ATxmega384C3@QFN64 [CX4023]  
ATxmega64A1@BGA100 [CX5055]  
ATxmega64A1U@CBGA100 [CX5055]  
ATxmega64A1U@VFBGA100 [CX5215]  
ATxmega64A3@TQFP64 [CX3044]  
ATxmega64A3U@TQFP64 [CX3044]  
ATxmega64A4@TQFP44 [CX3005]  
ATxmega64A4U@QFN44 [CX4018]  
ATxmega64B1@TQFP100 [CX3043]  
ATxmega64B3@TQFP64 [CX3044]  
ATxmega64C3@TQFP64 [CX3044]  
ATxmega64D3@TQFP64 [CX3044]  
ATxmega64D4@TQFP44 [CX3005]  
ATxmega8E5@UQFN32 [CX4084]  
T89C51SND1@TQFP80 [CX3018]  
T89F64@PLCC44 [CX2044]

## ATMEL W&M

### MICROCONTROLLER

AT89C5115@PLCC28 [CX2028]  
AT89C5115@TQFP32 [CX3001]

AT89C5115@SOIC28 [CX1033]  
AT89C51CC02@PLCC28 [CX2028]

AT89C51CC02@SOIC28 [CX1033]  
T89C5115@PLCC28 [CX2028]  
T89C5115@TQFP32 [CX3001]  
T89C51AC2@TQFP44 [CX3003]  
T89C51CC01@TQFP44 [CX3003]  
T89C51CC02@SOIC24 [CX1033]  
T89C51CC02@TQFP32 [CX3001]  
T89C51IB2@TQFP44 [CX3003]  
T89C51IC2@TQFP44 [CX3003]  
T89C51RB2@PLCC44 [CX2044]  
T89C51RC2 [CX0001]  
T89C51RC2@TQFP44 [CX3003]  
T89C51RD2@PLCC44 [CX2044]  
T89C51RD2@TQFP44 [CX3003]  
T89F64@PLCC44 [CX2044]  
TS87C51RB2 [CX0001]  
TS87C51RB2@TQFP44 [CX3002]  
TS87C51RC2@PLCC44 [CX2044]  
TS87C51RD2 [CX0001]  
TS87C51RD2@TQFP44 [CX3002]  
TS87C51U2@PLCC44 [CX2044]  
TS87C52X2 [CX0001]  
TS87C52X2@TQFP44 [CX3002]  
TS87C54X2@PLCC44 [CX2044]  
TS87C58X2 [CX0001]  
TS87C58X2@TQFP44 [CX3002]  
TSC87251G1 [CX0001]  
TSC87251G1A [CX0001]  
TSC87251G2D [CX0001]  
TSC87251G2D@TQFP44 [CX3003]  
TSC87C51@PLCC44 [CX2044]

AT89C51CC02@TQFP32 [CX3001]  
T89C5115@SOIC28 [CX1033]  
T89C51AC2@PLCC44 [CX2044]  
T89C51CC01@PLCC44 [CX2044]  
T89C51CC02@PLCC28 [CX2028]  
T89C51CC02@SOIC28 [CX1033]  
T89C51IB2@PLCC44 [CX2044]  
T89C51IC2@PLCC44 [CX2044]  
T89C51RB2 [CX0001]  
T89C51RB2@TQFP44 [CX3003]  
T89C51RC2@PLCC44 [CX2044]  
T89C51RD2 [CX0001]  
T89C51RD2@PLCC68 [CX2068]  
T89F64 [CX0001]  
T89F64@TQFP44 [CX3003]  
TS87C51RB2@PLCC44 [CX2044]  
TS87C51RC2 [CX0001]  
TS87C51RC2@TQFP44 [CX3002]  
TS87C51RD2@PLCC44 [CX2044]  
TS87C51U2 [CX0001]  
TS87C51U2@TQFP44 [CX3002]  
TS87C52X2@PLCC44 [CX2044]  
TS87C54X2 [CX0001]  
TS87C54X2@TQFP44 [CX3002]  
TS87C58X2@PLCC44 [CX2044]  
TSC87251A1@PLCC44 [CX2044]  
TSC87251G1@PLCC44 [CX2004]  
TSC87251G1A@PLCC44 [CX2044]  
TSC87251G2D@PLCC44 [CX2044]  
TSC87C51 [CX0001]  
TSC87C51@TQFP44 [CX3002]

## ATMEL-CUSTOM

### MICROCONTROLLER

ATMEGA48(ISP)(CAL) [CX0001]  
ATMEGA48PA(ISP)(CAL) [CX0001]  
ATMEGA48PV(ISP)(CAL) [CX0001]

ATMEGA48@TQFP32(CAL) [CX3061]  
ATMEGA48PA@TQFP32(CAL) [CX3061]  
ATMEGA48PV@TQFP32(CAL) [CX3061]

## ATMEL-CUSTOMER

### MICROCONTROLLER

AT90CAN128@QFN64 [CX4023]  
AT90CAN64@QFN64 [CX4023]

AT90CAN128@TQFP64 [CX3013]  
AT90CAN64@TQFP64 [CX3013]

## ATO

### E(E) PROM/FRAM/NVRAM

AFND1208U1@TSOP48 [CX1004-3]  
AFND5608S1@TSOP48 [CX1004-3]

AFND1G08U3@TSOP48 [CX1004-3]  
AFND5608U1@TSOP48 [CX1004-3]

## AUO

## E (E) PROM/FRAM/NVRAM

AUO-G1422.29@TQFN32 [CX4015]

AUO-G1422.2H@TQFN32 [CX4015]

## AUSTIN

### E (E) PROM/FRAM/NVRAM

AS8E512K8 [CX0001]

AS8E512K8@SOJ32 [CX1038]

## AXELITE

### E (E) PROM/FRAM/NVRAM

AX24C02A@DFN8 [CX4002]

AX24C02A@SOT23-5 [CX1041]

AX24C04A@DFN8 [CX4002]

AX24C04A@SOT23-5 [CX1041]

AX24C08A@DFN8 [CX4002]

AX24C08A@SOT23-5 [CX1041]

AX24C128A@DFN8 [CX4002]

AX24C128A@TSSOP8 [CX1059]

AX24C16A@SOP8 [CX1045]

AX24C16A@TSSOP8 [CX1059]

AX24C256A@SOP8 [CX1045]

AX24C32A@DFN8 [CX4002]

AX24C32A@TSSOP8 [CX1059]

AX24C64A@SOP8 [CX1045]

AX24C02A@SOP8 [CX1045]

AX24C02A@TSSOP8 [CX1059]

AX24C04A@SOP8 [CX1045]

AX24C04A@TSSOP8 [CX1059]

AX24C08A@SOP8 [CX1045]

AX24C08A@TSSOP8 [CX1059]

AX24C128A@SOP8 [CX1045]

AX24C16A@DFN8 [CX4002]

AX24C16A@SOT23-5 [CX1041]

AX24C256A@DFN8 [CX4002]

AX24C256A@TSSOP8 [CX1059]

AX24C32A@SOP8 [CX1045]

AX24C64A@DFN8 [CX4002]

AX24C64A@TSSOP8 [CX1059]

## AZOTEQ

### MICROCONTROLLER

IQS512@TSSOP20 [CX1067-4]

IQS530@TSSOP20 [CX1067-4]

IQS572@QFN28 [CX4083-3]

IQS525@QFN28 [CX4083-3]

IQS550@QFN48 [CX4021-2]

## BELLING

### E (E) PROM/FRAM/NVRAM

BL24C02 [CX0001]

BL24C02@TSSOP8 [CX1059]

BL24C04@SOP8 [CX1045]

BL24C08 [CX0001]

BL24C08@TSSOP8 [CX1059]

BL24C128@SOP8 [CX1045]

BL24C16 [CX0001]

BL24C16@TSSOP8 [CX1059]

BL24C256@SOP8 [CX1045]

BL24C32 [CX0001]

BL24C32@TSSOP8 [CX1059]

BL24C64@SOP8 [CX1045]

BL24C02@SOP8 [CX1045]

BL24C04 [CX0001]

BL24C04@TSSOP8 [CX1059]

BL24C08@SOP8 [CX1045]

BL24C128 [CX0001]

BL24C128@TSSOP8 [CX1059]

BL24C16@SOP8 [CX1045]

BL24C256 [CX0001]

BL24C256@TSSOP8 [CX1059]

BL24C32@SOP8 [CX1045]

BL24C64 [CX0001]

BL24C64@TSSOP8 [CX1059]

## BENCHMARQ

### E (E) PROM/FRAM/NVRAM

BQ3285 [CX0001]	BQ3287 [CX0001]
BQ3287A [CX0001]	BQ4010 [CX0001]
BQ4010Y [CX0001]	BQ4011 [CX0001]
BQ4011Y [CX0001]	BQ4013 [CX0001]
BQ4013Y [CX0001]	BQ4014 [CX0001]
BQ4014Y [CX0001]	BQ4015 [CX0001]
BQ4015Y [CX0001]	BQ4822 [CX0001]
BQ4822Y [CX0001]	BQ4830Y [CX0001]
BQ4832Y [CX0001]	BQ4842Y [CX0001]

## BERGMICRO

### E (E) PROM/FRAM/NVRAM

BG25Q16A [CX0001]	BG25Q16A@SOP8 [CX1044#1]
BG25Q40A [CX0001]	BG25Q40A@SOP8[150mil] [CX1045#1]
BG25Q40A@SOP8[200mil] [CX1044#1]	BG25Q40A@WSON8 [CX4005#1]
BG25Q80A [CX0001]	BG25Q80A@SOP8[150mil] [CX1045#1]
BG25Q80A@SOP8[200mil] [CX1044#1]	BG25Q80A@WSON8 [CX4005#1]

## BJX

### E (E) PROM/FRAM/NVRAM

BJX24LC02 [CX0001]	BJX24LC02@SOIC8 [CX1045]
BJX24LC02@TSSOP8 [CX1059]	BJX24LC04 [CX0001]
BJX24LC04@SOIC8 [CX1045]	BJX24LC04@TSSOP8 [CX1059]
BJX24LC08 [CX0001]	BJX24LC08@SOIC8 [CX1045]
BJX24LC08@TSSOP8 [CX1059]	BJX24LC16 [CX0001]
BJX24LC16@SOIC8 [CX1045]	BJX24LC16@TSSOP8 [CX1059]

## BMT

### E (E) PROM/FRAM/NVRAM

BM29LV160B@FBGA48 [CX5043]	BM29LV160B@TSOP48 [CX1004]
BM29LV160T@FBGA48 [CX5043]	BM29LV160T@TSOP48 [CX1004]

## BOCH

### MICROCONTROLLER

CY8C24533 [CX0001]

## Bookly Micro

### E (E) PROM/FRAM/NVRAM

24C02 [CX0001]	24C02@DFN8 [CX4002]
----------------	---------------------

24C02@MSOP8 [CX1015]  
24C02@TSSOP8 [CX1059]  
24C04@DFN8 [CX4002]  
24C04@SOIC8 [CX1045]  
24C08 [CX0001]  
24C08@MSOP8 [CX1015]  
24C08@TSSOP8 [CX1059]  
24C16@DFN8 [CX4002]  
24C16@SOIC8 [CX1045]

24C02@SOIC8 [CX1045]  
24C04 [CX0001]  
24C04@MSOP8 [CX1015]  
24C04@TSSOP8 [CX1059]  
24C08@DFN8 [CX4002]  
24C08@SOIC8 [CX1045]  
24C16 [CX0001]  
24C16@MSOP8 [CX1015]  
24C16@TSSOP8 [CX1059]

## BRIGHT

### E (E) PROM/FRAM/NVRAM

BM29F040 [CX0001]  
BM29F040@TSOP32 [CX1002]  
BM29F400B@TSOP48 [CX1004]  
BM29F400T@TSOP48 [CX1004]

BM29F040@PLCC32 [CX2032]  
BM29F400B@PSOP44 [CX1014]  
BM29F400T@PSOP44 [CX1014]

## CATALYST

### E (E) PROM/FRAM/NVRAM

CAT1021(L) [CX0001]  
CAT1021(R)@MSOP8 [CX1059]  
CAT1021(U)@TSSOP8 [CX1059]  
CAT1021(Y)@TSSOP8 [CX1059]  
CAT1022(L) [CX0001]  
CAT1022(R)@MSOP8 [CX1059]  
CAT1022(U)@TSSOP8 [CX1059]  
CAT1022(Y)@TSSOP8 [CX1059]  
CAT1023(L) [CX0001]  
CAT1023(R)@MSOP8 [CX1059]  
CAT1023(U)@TSSOP8 [CX1059]  
CAT1023(Y)@TSSOP8 [CX1059]  
CAT1024(L) [CX0001]  
CAT1024(R)@MSOP8 [CX1059]  
CAT1024(U)@TSSOP8 [CX1059]  
CAT1024(Y)@TSSOP8 [CX1059]  
CAT1025(L) [CX0001]  
CAT1025(R)@MSOP8 [CX1059]  
CAT1025(U)@TSSOP8 [CX1059]  
CAT1025(Y)@TSSOP8 [CX1059]  
CAT1026(L) [CX0001]  
CAT1026(R)@MSOP8 [CX1059]  
CAT1026(U)@TSSOP8 [CX1059]  
CAT1026(Y)@TSSOP8 [CX1059]  
CAT1027(L) [CX0001]  
CAT1027(R)@MSOP8 [CX1059]  
CAT1027(U)@TSSOP8 [CX1059]  
CAT1027(Y)@TSSOP8 [CX1059]  
CAT1161(J)@SOIC8 [CX1045]  
CAT1162(J)@SOIC8 [CX1045]  
CAT1163(J)@SOIC8 [CX1045]  
CAT1320 [CX0001]  
CAT1320@TDFN8 [CX0001]  
CAT1321 [CX0001]

CAT1021(P) [CX0001]  
CAT1021(S)@SOIC8 [CX1045]  
CAT1021(V)@SOIC8 [CX1045]  
CAT1021(Z)@MSOP8 [CX1059]  
CAT1022(P) [CX0001]  
CAT1022(S)@SOIC8 [CX1045]  
CAT1022(V)@SOIC8 [CX1045]  
CAT1022(Z)@MSOP8 [CX1059]  
CAT1023(P) [CX0001]  
CAT1023(S)@SOIC8 [CX1045]  
CAT1023(V)@SOIC8 [CX1045]  
CAT1023(Z)@MSOP8 [CX1059]  
CAT1024(P) [CX0001]  
CAT1024(S)@SOIC8 [CX1045]  
CAT1024(V)@SOIC8 [CX1045]  
CAT1024(Z)@MSOP8 [CX1059]  
CAT1025(P) [CX0001]  
CAT1025(S)@SOIC8 [CX1045]  
CAT1025(V)@SOIC8 [CX1045]  
CAT1025(Z)@MSOP8 [CX1059]  
CAT1026(P) [CX0001]  
CAT1026(S)@SOIC8 [CX1045]  
CAT1026(V)@SOIC8 [CX1045]  
CAT1026(Z)@MSOP8 [CX1059]  
CAT1027(P) [CX0001]  
CAT1027(S)@SOIC8 [CX1045]  
CAT1027(V)@SOIC8 [CX1045]  
CAT1027(Z)@MSOP8 [CX1059]  
CAT1161(P) [CX0001]  
CAT1162(P) [CX0001]  
CAT1163(P) [CX0001]  
CAT1320@SOIC8 [CX1045]  
CAT1320@TSSOP8 [CX1059]  
CAT1321@SOIC8 [CX1045]

CAT1321@TDFN8 [CX0001]                   CAT1321@TSSOP8 [CX1059]  
CAT14002@SOIC8 [CX1045]                   CAT14004@SOIC8 [CX1045]  
CAT14008@SOIC8 [CX1045]                   CAT14016@SOIC8 [CX1045]  
CAT15002@SOIC8 [CX1045]                   CAT15004@SOIC8 [CX1045]  
CAT15008@SOIC8 [CX1045]                   CAT15016@SOIC8 [CX1045]  
CAT1640 [CX0001]                            CAT1640@SOIC8 [CX1045]  
CAT1640@TDFN8 [CX0001]                   CAT1640@TSSOP8 [CX1059]  
CAT1641 [CX0001]                            CAT1641@SOIC8 [CX1045]  
CAT1641@TDFN8 [CX0001]                   CAT1641@TSSOP8 [CX1059]  
CAT2210 [CX0001]                            CAT2210@SOIC16 [CX1033]  
CAT2210I [CX0001]                           CAT2210I@SOIC16 [CX1033]  
CAT2212 [CX0001]                            CAT2212@SOIC20 [CX1033]  
CAT2212I [CX0001]                           CAT2212I@SOIC20 [CX1033]  
CAT22C10 [CX0001]                           CAT22C10@SOIC16 [CX1033]  
CAT22C10I [CX0001]                          CAT22C10I@SOIC16 [CX1033]  
CAT22C12 [CX0001]                            CAT22C12@SOIC20 [CX1033]  
CAT22C12I [CX0001]                          CAT22C12I@SOIC20 [CX1033]  
CAT24AA01@SOIC8 [CX1045]                   CAT24AA01@TSOT-23 [CX1041]  
CAT24AA02@SOIC8 [CX1045]                   CAT24AA02@TSOT-23 [CX1041]  
CAT24AA04@SOIC8 [CX1045]                   CAT24AA04@TSOT-23 [CX1041]  
CAT24AA08@SOIC8 [CX1045]                   CAT24AA08@TSOT-23 [CX1041]  
CAT24AA16@SOIC8 [CX1045]                   CAT24AA16@TSOT-23 [CX1041]  
CAT24AC128 [CX0001]                          CAT24AC128@SOIC8 [CX1045]  
CAT24AC128@TSSOP14 [CX1000]               CAT24AC128@TSSOP8 [CX1059]  
CAT24AC128@UDFN8 [CX4002]                 CAT24C00 [CX0001]  
CAT24C00@SOIC8 [CX1045]                    CAT24C00@TSSOP8 [CX1059]  
CAT24C01 [CX0001]                            CAT24C01@MSOP8 [CX1015]  
CAT24C01@SOIC14 [CX1030]                   CAT24C01@SOIC8 [CX1045]  
CAT24C01@TDFN8 [CX4002]                   CAT24C01@TSOT-23 [CX1041]  
CAT24C01@TSSOP8 [CX1059]                  CAT24C01B(J)@SOIC8 [CX1045]  
CAT24C01B(L) [CX0001]                       CAT24C01B(P) [CX0001]  
CAT24C01B(R)@MSOP8 [CX1059]               CAT24C01B(U)@TSSOP8 [CX1059]  
CAT24C01B(W)@SOIC8 [CX1045]               CAT24C01B(Y)@TSSOP8 [CX1059]  
CAT24C01B(Z)@MSOP8 [CX1059]               CAT24C02 [CX0001]  
CAT24C02@MSOP8 [CX1015]                    CAT24C02@SOIC14 [CX1030]  
CAT24C02@SOIC8 [CX1045]                    CAT24C02@TDFN8 [CX4002]  
CAT24C02@TSOT-23 [CX1041]                 CAT24C02@TSSOP8 [CX1059]  
CAT24C021 [CX0001]                          CAT24C022 [CX0001]  
CAT24C023 [CX0001]                          CAT24C03 [CX0001]  
CAT24C03@SOIC8 [CX1045]                    CAT24C03@TDFN8 [CX4002]  
CAT24C03@TSSOP8 [CX1059]                  CAT24C04 [CX0001]  
CAT24C04@MSOP8 [CX1015]                    CAT24C04@SOIC14 [CX1030]  
CAT24C04@SOIC8 [CX1045]                    CAT24C04@TDFN8 [CX4002]  
CAT24C04@TSOT-23 [CX1041]                 CAT24C04@TSSOP8 [CX1059]  
CAT24C041 [CX0001]                          CAT24C042 [CX0001]  
CAT24C043 [CX0001]                          CAT24C05 [CX0001]  
CAT24C05@SOIC8 [CX1045]                    CAT24C05@TDFN8 [CX4002]  
CAT24C05@TSSOP8 [CX1059]                  CAT24C08 [CX0001]  
CAT24C08@MSOP8 [CX1015]                    CAT24C08@SOIC14 [CX1030]  
CAT24C08@SOIC8 [CX1045]                    CAT24C08@TDFN8 [CX4002]  
CAT24C08@TSOT-23 [CX1041]                 CAT24C08@TSSOP8 [CX1059]  
CAT24C081 [CX0001]                          CAT24C082 [CX0001]  
CAT24C083 [CX0001]                          CAT24C08I [CX0001]  
CAT24C08I@SOIC8 [CX1045]                   CAT24C09 [CX0001]  
CAT24C09@SOIC8 [CX1045]                    CAT24C09@TDFN8 [CX4002]  
CAT24C09@TSSOP8 [CX1059]                  CAT24C128 [CX0001]  
CAT24C128@SOIC8 [CX1045]                   CAT24C128@TSSOP8 [CX1059]  
CAT24C128@UDFN8 [CX4002]                  CAT24C16 [CX0001]  
CAT24C16@SOIC14 [CX1030]                   CAT24C16@SOIC8 [CX1045]

CAT24C16@TDFN8 [CX4002]  
CAT24C161 [CX0001]  
CAT24C163 [CX0001]  
CAT24C164@SOIC8 [CX1045]  
CAT24C16I [CX0001]  
CAT24C208(J)@SOIC8 [CX1045]  
CAT24C208(P) [CX0001]  
CAT24C208(U)@TSSOP8 [CX1059]  
CAT24C208(Y)@TSSOP8 [CX1059]  
CAT24C21 [CX0001]  
CAT24C21@TSSOP8 [CX1059]  
CAT24C256@SOIC8 [CX1045]  
CAT24C32@SOIC8 [CX1045]  
CAT24C44 [CX0001]  
CAT24C64 [CX0001]  
CAT24F32 [CX0001]  
CAT24F32@TSSOP8 [CX1059]  
CAT24F32A@SOIC8 [CX1045]  
CAT24FC01 [CX0001]  
CAT24FC01@SOIC8 [CX1045]  
CAT24FC01@TSSOP8 [CX1059]  
CAT24FC02@SOIC14 [CX1030]  
CAT24FC02@TDFN8 [CX4002]  
CAT24FC16 [CX0001]  
CAT24FC16@SOIC8 [CX1045]  
CAT24FC16@TSSOP8 [CX1059]  
CAT24FC17@SOIC8 [CX1045]  
CAT24FC17@TSSOP8 [CX1059]  
CAT24FC256@SOIC8 [CX1045]  
CAT24FC256@TSSOP8 [CX1059]  
CAT24FC32@SOIC8 [CX1045]  
CAT24FC32@TSSOP8 [CX1059]  
CAT24FC64@SOIC8 [CX1045]  
CAT24FC64@TSSOP8 [CX1059]  
CAT24FC65@SOIC8 [CX1045]  
CAT24FC65@TSSOP8 [CX1059]  
CAT24FC66@SOIC8 [CX1045]  
CAT24FC66@TSSOP8 [CX1059]  
CAT24LC02@SOIC8 [CX1045]  
CAT24LC02@TSSOP8 [CX1059]  
CAT24WC01@SOIC8 [CX1045]  
CAT24WC02 [CX0001]  
CAT24WC02@TSSOP8 [CX1059]  
CAT24WC03@SOIC8 [CX1045]  
CAT24WC04 [CX0001]  
CAT24WC04@TSSOP8 [CX1059]  
CAT24WC05@SOIC8 [CX1045]  
CAT24WC08 [CX0001]  
CAT24WC08@TSSOP8 [CX1059]  
CAT24WC09@SOIC8 [CX1045]  
CAT24WC128 [CX0001]  
CAT24WC128@TSSOP8 [CX1059]  
CAT24WC129@SOIC8 [CX1045]  
CAT24WC16@SOIC8 [CX1045]  
CAT24WC164 [CX0001]  
CAT24WC164@TSSOP8 [CX1059]  
CAT24WC17@SOIC8 [CX1045]  
CAT24WC256 [CX0001]  
CAT24WC257 [CX0001]  
CAT24C16@TSSOP8 [CX1059]  
CAT24C162 [CX0001]  
CAT24C164 [CX0001]  
CAT24C164@TSSOP8 [CX1059]  
CAT24C16I@SOIC8 [CX1045]  
CAT24C208(L) [CX0001]  
CAT24C208(R)@MSOP8 [CX1015]  
CAT24C208(W)@SOIC8 [CX1045]  
CAT24C208(Z)@MSOP8 [CX1015]  
CAT24C21@SOIC8 [CX1045]  
CAT24C256 [CX0001]  
CAT24C32 [CX0001]  
CAT24C32@UDFN8 [CX4002]  
CAT24C44@SOIC8 [CX1045]  
CAT24C64@SOIC8 [CX1045]  
CAT24F32@SOIC8 [CX1045]  
CAT24F32A [CX0001]  
CAT24F32A@TSSOP8 [CX1059]  
CAT24FC01@SOIC14 [CX1030]  
CAT24FC01@TDFN8 [CX4002]  
CAT24FC02 [CX0001]  
CAT24FC02@SOIC8 [CX1045]  
CAT24FC02@TSSOP8 [CX1059]  
CAT24FC16@SOIC14 [CX1030]  
CAT24FC16@TDFN8 [CX4002]  
CAT24FC17 [CX0001]  
CAT24FC17@TDFN8 [CX4002]  
CAT24FC256 [CX0001]  
CAT24FC256@TDFN8 [CX4005]  
CAT24FC32 [CX0001]  
CAT24FC32@TDFN8 [CX4005]  
CAT24FC64 [CX0001]  
CAT24FC64@TDFN8 [CX4005]  
CAT24FC65 [CX0001]  
CAT24FC65@TDFN8 [CX4005]  
CAT24FC66 [CX0001]  
CAT24FC66@TDFN8 [CX4005]  
CAT24LC02 [CX0001]  
CAT24LC02@TDFN8 [CX4002]  
CAT24WC01 [CX0001]  
CAT24WC01@TSSOP8 [CX1059]  
CAT24WC02@SOIC8 [CX1045]  
CAT24WC03 [CX0001]  
CAT24WC03@TSSOP8 [CX1059]  
CAT24WC04@SOIC8 [CX1045]  
CAT24WC05 [CX0001]  
CAT24WC05@TSSOP8 [CX1059]  
CAT24WC08@SOIC8 [CX1045]  
CAT24WC09 [CX0001]  
CAT24WC09@TSSOP8 [CX1059]  
CAT24WC128@SOIC8 [CX1045]  
CAT24WC129 [CX0001]  
CAT24WC16 [CX0001]  
CAT24WC16@TSSOP8 [CX1059]  
CAT24WC164@SOIC8 [CX1045]  
CAT24WC17 [CX0001]  
CAT24WC17@TSSOP8 [CX1059]  
CAT24WC256@SOIC8 [CX1045]  
CAT24WC257@SOIC8 [CX1045]

CAT24WC32 [CX0001] CAT24WC32@SOIC8 [CX1045]  
CAT24WC33 [CX0001] CAT24WC33@SOIC8 [CX1045]  
CAT24WC64 [CX0001] CAT24WC64@SOIC8 [CX1045]  
CAT24WC64@TSSOP8 [CX1059] CAT24WC65 [CX0001]  
CAT24WC65@SOIC8 [CX1045] CAT24WC66 [CX0001]  
CAT24WC66@SOIC8 [CX1045] CAT25010 [CX0001]  
CAT25010(S)@SOIC8 [CX1044] CAT25010(U)@TSSOP8 [CX1045]  
CAT25020 [CX0001] CAT25020(S)@SOIC8 [CX1044]  
CAT25020(U)@TSSOP8 [CX1045] CAT25040 [CX0001]  
CAT25040(S)@SOIC8 [CX1044] CAT25040(U)@TSSOP8 [CX1045]  
CAT25080 [CX0001] CAT25080@SOIC8 [CX1045]  
CAT25080@TDFN8 [CX4002] CAT25080@TSSOP8 [CX1059]  
CAT25080@UDFN8 [CX0001] CAT25128 [CX0001]  
CAT25128@SOIC8 [CX1045] CAT25128@TDFN8 [CX4002]  
CAT25128@TSSOP8 [CX1059] CAT25160 [CX0001]  
CAT25160@SOIC8 [CX1045] CAT25160@TDFN8 [CX4002]  
CAT25160@TSSOP8 [CX1059] CAT25160@UDFN8 [CX0001]  
CAT25256 [CX0001] CAT25256@SOIC8 [CX1045]  
CAT25256@TDFN8 [CX4002] CAT25256@TSSOP8 [CX1059]  
CAT25320 [CX0001] CAT25320@SOIC8 [CX1045]  
CAT25320@TDFN8 [CX4002] CAT25320@TSSOP8 [CX1059]  
CAT25640 [CX0001] CAT25640@SOIC8 [CX1045]  
CAT25640@TDFN8 [CX4002] CAT25640@TSSOP8 [CX1059]  
CAT25C01 [CX0001] CAT25C01@SOIC16 [CX1016]  
CAT25C01@SOIC8 [CX1045] CAT25C01@TSSOP14 [CX1059]  
CAT25C01@TSSOP8 [CX1059] CAT25C02 [CX0001]  
CAT25C02@SOIC16 [CX1016] CAT25C02@SOIC8 [CX1045]  
CAT25C02@TSSOP14 [CX1000] CAT25C02@TSSOP8 [CX1059]  
CAT25C03 [CX0001] CAT25C03@SOIC8 [CX1045]  
CAT25C03@TSSOP14 [CX1000] CAT25C03@TSSOP8 [CX1059]  
CAT25C04 [CX0001] CAT25C04@SOIC16 [CX1016]  
CAT25C04@SOIC8 [CX1045] CAT25C04@TSSOP14 [CX1000]  
CAT25C04@TSSOP8 [CX1059] CAT25C05 [CX0001]  
CAT25C05@SOIC8 [CX1045] CAT25C05@TSSOP14 [CX1000]  
CAT25C05@TSSOP8 [CX1059] CAT25C08 [CX0001]  
CAT25C08@SOIC16 [CX1016] CAT25C08@SOIC8 [CX1045#1]  
CAT25C08@TSSOP14 [CX1000] CAT25C08@TSSOP8 [CX1059#1]  
CAT25C09 [CX0001] CAT25C09@SOIC8 [CX1045#1]  
CAT25C09@TSSOP14 [CX1000] CAT25C09@TSSOP8 [CX1059#1]  
CAT25C11 [CX0001] CAT25C11@SOIC8 [CX1045]  
CAT25C11@TSSOP14 [CX1000] CAT25C11@TSSOP8 [CX1059]  
CAT25C128 [CX0001] CAT25C128@SOIC16 [CX1016]  
CAT25C128@SOIC8[150 mil] [CX1045#1]  
CAT25C128@SOIC8[208 mil] [CX1044]  
CAT25C128@TSSOP14 [CX1000] CAT25C128@TSSOP20 [CX1000]  
CAT25C16 [CX0001] CAT25C16@SOIC16 [CX1016]  
CAT25C16@SOIC8 [CX1045#1] CAT25C16@TSSOP14 [CX1000]  
CAT25C16@TSSOP8 [CX1059#1] CAT25C17 [CX0001]  
CAT25C17@SOIC8 [CX1045#1] CAT25C17@TSSOP14 [CX1000]  
CAT25C17@TSSOP8 [CX1059#1] CAT25C256 [CX0001]  
CAT25C256@SOIC16 [CX1016]  
CAT25C256@SOIC8[150 mil] [CX1045#1]  
CAT25C256@SOIC8[208 mil] [CX1044]  
CAT25C256@TSSOP14 [CX1000] CAT25C256@TSSOP20 [CX1000]  
CAT25C32 [CX0001] CAT25C32@SOIC8 [CX1045#1]  
CAT25C32@TSSOP14 [CX1000] CAT25C32@TSSOP20 [CX1000]  
CAT25C33 [CX0001] CAT25C33@SOIC8 [CX1045#1]  
CAT25C33@TSSOP14 [CX1000] CAT25C64 [CX0001]  
CAT25C64@SOIC8 [CX1045#1] CAT25C64@TSSOP14 [CX1000]



CAT25C64@TSSOP20 [CX1000]  
CAT25C65@SOIC8 [CX1045#1]  
CAT27010 [CX0001]  
CAT27010@TSOP32 [CX1002]  
CAT27256 [CX0001]  
CAT27512@PLCC32 [CX2032]  
CAT27C16A [CX0001]  
CAT27C210@PLCC44 [CX2044]  
CAT27HC256@PLCC32 [CX2032]  
CAT27HC256I@PLCC32 [CX2032]  
CAT28C16A@PLCC32 [CX2032]  
CAT28C16AI [CX0001]  
CAT28C16AI@SOIC24 [CX1033]  
CAT28C17A@PLCC32 [CX2032]  
CAT28C17AI@PLCC32 [CX2032]  
CAT28C256@PLCC32 [CX2032]  
CAT28C256I [CX0001]  
CAT28C256I@TSOP28 [CX1024]  
CAT28C257@PLCC32 [CX2032]  
CAT28C512 [CX0001]  
CAT28C512@TSOP32 [CX1002]  
CAT28C513@PLCC32 [CX2032]  
CAT28C64A@PLCC32 [CX2032]  
CAT28C64AI [CX0001]  
CAT28C64AI@SOIC28 [CX1033]  
CAT28C64B@PLCC32 [CX2032]  
CAT28C64B@TSOP28 [CX1024]  
CAT28C64BI@PLCC32 [CX2032]  
CAT28C65B [CX0001]  
CAT28C65B@TSOP28 [CX1024]  
CAT28C65BI@PLCC32 [CX2032]  
CAT28F001N-B@PLCC32 [CX2032]  
CAT28F001P-B [CX0001]  
CAT28F001T-B@TSOP32 [CX1002]  
CAT28F002B [CX0001]  
CAT28F002T [CX0001]  
CAT28F010 [CX0001]  
CAT28F010(REVERSE)@TSOP32 [CX1002]  
CAT28F010@PLCC32 [CX2032]  
CAT28F010I [CX0001]  
CAT28F010I(REVERSE)@TSOP32 [CX1002]  
CAT28F010I@PLCC32 [CX2032]  
CAT28F020 [CX0001]  
CAT28F020(REVERSE)@TSOP32 [CX1002]  
CAT28F020@PLCC32 [CX2032]  
CAT28F020I [CX0001]  
CAT28F020I(REVERSE)@TSOP32 [CX1002]  
CAT28F020I@PLCC32 [CX2032]  
CAT28F102 [CX0001]  
CAT28F102@TSOP40 [CX1005]  
CAT28F512(REVERSE)@TSOP32 [CX1002]  
CAT28F512@PLCC32 [CX2032]  
CAT28F512I [CX0001]  
CAT28F512I(REVERSE)@TSOP32 [CX1002]  
CAT28F512I@PLCC32 [CX2032]  
CAT28LV256 [CX0001]  
CAT28LV256@TSOP28 [CX1024]  
CAT28LV64@PLCC32 [CX2032]  
CAT28LV65 [CX0001]  
CAT25C65 [CX0001]  
CAT25C65@TSSOP14 [CX1000]  
CAT27010@PLCC32 [CX2032]  
CAT27128A [CX0001]  
CAT27512 [CX0001]  
CAT2764A [CX0001]  
CAT27C210 [CX0001]  
CAT27HC256 [CX0001]  
CAT27HC256I [CX0001]  
CAT28C16A [CX0001]  
CAT28C16A@SOIC24 [CX1033]  
CAT28C16AI@PLCC32 [CX2032]  
CAT28C17A [CX0001]  
CAT28C17AI [CX0001]  
CAT28C256 [CX0001]  
CAT28C256@TSOP28 [CX1024]  
CAT28C256I@PLCC32 [CX2032]  
CAT28C257 [CX0001]  
CAT28C257@TSOP28 [CX1024]  
CAT28C512@PLCC32 [CX2032]  
CAT28C512@TSOP40 [CX1006]  
CAT28C64A [CX0001]  
CAT28C64A@SOIC28 [CX1033]  
CAT28C64AI@PLCC32 [CX2032]  
CAT28C64B [CX0001]  
CAT28C64B@SOIC28 [CX1033]  
CAT28C64BI [CX0001]  
CAT28C64BI@TSOP28 [CX1024]  
CAT28C65B@PLCC32 [CX2032]  
CAT28C65BI [CX0001]  
CAT28C65BI@TSOP28 [CX1024]  
CAT28F001N-T@PLCC32 [CX2032]  
CAT28F001P-T [CX0001]  
CAT28F001T-T@TSOP32 [CX1002]  
CAT28F002B@TSOP40 [CX1006]  
CAT28F002T@TSOP40 [CX1006]  
CAT28F010@TSOP32 [CX1002]  
CAT28F010I@TSOP32 [CX1002]  
CAT28F020@TSOP32 [CX1002]  
CAT28F020I@TSOP32 [CX1002]  
CAT28F102@PLCC44 [CX2044]  
CAT28F512 [CX0001]  
CAT28F512@TSOP32 [CX1002]  
CAT28LV256@PLCC32 [CX2032]  
CAT28LV64 [CX0001]  
CAT28LV64@TSOP28 [CX1024]  
CAT28LV65@PLCC32 [CX2032]

CAT28LV65@TSOP28 [CX1024]  
CAT33C101(08bit)@SOIC8 [CX1045]  
CAT33C101(16bit)@SOIC8 [CX1045]  
CAT33C101H(08bit)@SOIC8 [CX1045]  
CAT33C101H(16bit)@SOIC8 [CX1045]  
CAT33C101I(08bit)@SOIC8 [CX1045]  
CAT33C101I(16bit)@SOIC8 [CX1045]  
CAT33C104(08bit)@SOIC8 [CX1045]  
CAT33C104(16bit)@SOIC8 [CX1045]  
CAT33C104I(08bit)@SOIC8 [CX1045]  
CAT33C104I(16bit)@SOIC8 [CX1045]  
CAT34AC02@SOIC8 [CX1045]  
CAT34C02 [CX0001]  
CAT34C02@TDFN8 [CX4002]  
CAT34FC02 [CX0001]  
CAT34FC02@TDFN8 [CX4002]  
CAT34RC02 [CX0001]  
CAT34RC02@TDFN8 [CX4002]  
CAT34TS02@TDFN8 [CX4002]  
CAT34WC02@SOIC8 [CX1045]  
CAT34WC02@TSSOP8 [CX1059]  
CAT35C102H [CX0001]  
CAT35C104(08bit) [CX0001]  
CAT35C104(16bit) [CX0001]  
CAT35C104H(08bit) [CX0001]  
CAT35C104I(08bit) [CX0001]  
CAT35C104I(16bit) [CX0001]  
CAT59C11 [CX0001]  
CAT59C11A [CX0001]  
CAT59C11H [CX0001]  
CAT59C11I [CX0001]  
CAT64LC10(J)@SOIC8 [CX1045]  
CAT64LC10(S)@SOIC8 [CX1045]  
CAT64LC10(UR)@TSSOP8 [CX1059]  
CAT64LC20(P) [CX0001]  
CAT64LC20(U)@TSSOP8 [CX1000]  
CAT64LC40(J)@SOIC8 [CX1045]  
CAT64LC40(S)@SOIC8 [CX1045]  
CAT64LC40(UR)@TSSOP8 [CX1000]  
CAT93C46(08bit)(J)@SOIC8 [CX1045]  
CAT93C46(08bit)(K)@SOIC8 [CX1044]  
CAT93C46(08bit)(S)@SOIC8 [CX1045]  
CAT93C46(08bit)(U)@TSSOP8 [CX1059]  
CAT93C46(16bit) [CX0001]  
CAT93C46(16bit)(J)@SOIC8 [CX1045]  
CAT93C46(16bit)(K)@SOIC8 [CX1044]  
CAT93C46(16bit)(S)@SOIC8 [CX1045]  
CAT93C46(16bit)(U)@TSSOP8 [CX1059]  
CAT93C46A [CX0001]  
CAT93C46R(08bit)(V)@SOIC8 [CX1045]  
CAT93C46R(08bit)(VP2)@TDFN8 [CX4002]  
CAT93C46R(08bit)(W)@SOIC8 [CX1045]  
CAT93C46R(08bit)(X)@SOIC8 [CX1045]  
CAT93C46R(08bit)(Y)@TSSOP8 [CX1059]  
CAT93C46R(16bit)(V)@SOIC8 [CX1045]  
CAT93C46R(16bit)(VP2)@TDFN8 [CX4002]  
CAT93C46R(16bit)(W)@SOIC8 [CX1045]  
CAT93C46R(16bit)(X)@SOIC8 [CX1045]  
CAT93C46R(16bit)(Y)@TSSOP8 [CX1059]  
CAT33C101(08bit) [CX0001]  
CAT33C101(16bit) [CX0001]  
CAT33C101H(08bit) [CX0001]  
CAT33C101H(16bit) [CX0001]  
CAT33C101I(08bit) [CX0001]  
CAT33C101I(16bit) [CX0001]  
CAT33C104(08bit) [CX0001]  
CAT33C104(16bit) [CX0001]  
CAT33C104I(08bit) [CX0001]  
CAT33C104I(16bit) [CX0001]  
CAT34AC02 [CX0001]  
CAT34AC02@TSSOP8 [CX1059]  
CAT34C02@SOIC8 [CX1045]  
CAT34C02@TSSOP8 [CX1059]  
CAT34FC02@SOIC8 [CX1045]  
CAT34FC02@TSSOP8 [CX1059]  
CAT34RC02@SOIC8 [CX1045]  
CAT34RC02@TSSOP8 [CX1059]  
CAT34WC02 [CX0001]  
CAT34WC02@TDFN8 [CX4002]  
CAT35C102 [CX0001]  
CAT35C102I [CX0001]  
CAT35C104(08bit)@SOIC8 [CX1045]  
CAT35C104(16bit)@SOIC8 [CX1045]  
CAT35C104H(08bit)@SOIC8 [CX1045]  
CAT35C104I(08bit)@SOIC8 [CX1045]  
CAT35C104I(16bit)@SOIC8 [CX1045]  
CAT59C11@SOIC8 [CX1045]  
CAT59C11A@SOIC8 [CX1045]  
CAT59C11H@SOIC8 [CX1045]  
CAT59C11I@SOIC8 [CX1045]  
CAT64LC10(P) [CX0001]  
CAT64LC10(U)@TSSOP8 [CX1059]  
CAT64LC20(J)@SOIC8 [CX1045]  
CAT64LC20(S)@SOIC8 [CX1045]  
CAT64LC20(UR)@TSSOP8 [CX1000]  
CAT64LC40(P) [CX0001]  
CAT64LC40(U)@TSSOP8 [CX1000]  
CAT93C46(08bit) [CX0001]  
CAT93C46R(08bit) [CX0001]

CAT93C46R-16 [CX0001]	CAT93C56(08bit) [CX0001]
CAT93C56(08bit)@SOIC8 [CX1045]	CAT93C56(08bit)@SSOP8 [CX1044]
CAT93C56(08bit)@TDFN8 [CX4002]	CAT93C56(08bit)@TSSOP8 [CX1059]
CAT93C56(08bit)@UDFN8 [CX4003]	CAT93C56(16bit) [CX0001]
CAT93C56(16bit)@SOIC8 [CX1045]	CAT93C56A [CX0001]
CAT93C57 [CX0001]	CAT93C66(08bit) [CX0001]
CAT93C66(08bit)@SOIC8 [CX1045]	CAT93C66(08bit)@TSSOP8 [CX1059]
CAT93C66(16bit) [CX0001]	CAT93C66(16bit)@SOIC8 [CX1045]
CAT93C66(16bit)@TSSOP8 [CX1059]	CAT93C66A [CX0001]
CAT93C76(08bit) [CX0001]	
CAT93C76(08bit)(J)@SOIC8 [CX1045]	
CAT93C76(08bit)(K)@SOIC8 [CX1044]	
CAT93C76(08bit)(S)@SOIC8 [CX1045]	
CAT93C76(08bit)(U)@TSSOP8 [CX1059]	
CAT93C76(16bit) [CX0001]	
CAT93C76(16bit)(J)@SOIC8 [CX1045]	
CAT93C76(16bit)(K)@SOIC8 [CX1044]	
CAT93C76(16bit)(S)@SOIC8 [CX1045]	
CAT93C76(16bit)(U)@TSSOP8 [CX1059]	
CAT93C86(08bit) [CX0001]	
CAT93C86(08bit)(J)@SOIC8 [CX1045]	
CAT93C86(08bit)(K)@SOIC8 [CX1044]	
CAT93C86(08bit)(S)@SOIC8 [CX1045]	
CAT93C86(08bit)(U)@TSSOP8 [CX1059]	
CAT93C86(16bit) [CX0001]	
CAT93C86(16bit)(J)@SOIC8 [CX1045]	
CAT93C86(16bit)(K)@SOIC8 [CX1044]	
CAT93C86(16bit)(S)@SOIC8 [CX1045]	
CAT93C86(16bit)(U)@TSSOP8 [CX1059]	
CAT93H46(08bit) [CX0001]	
CAT93H46(08bit)(J)@SOIC8 [CX1045]	
CAT93H46(08bit)(K)@SOIC8 [CX1044]	
CAT93H46(08bit)(S)@SOIC8 [CX1045]	
CAT93H46(08bit)(U)@TSSOP8 [CX1059]	
CAT93H46(16bit) [CX0001]	
CAT93H46(16bit)(J)@SOIC8 [CX1045]	
CAT93H46(16bit)(K)@SOIC8 [CX1044]	
CAT93H46(16bit)(S)@SOIC8 [CX1045]	
CAT93H46(16bit)(U)@TSSOP8 [CX1059]	
CAT93HC46(08bit) [CX0001]	
CAT93HC46(08bit)(J)@SOIC8 [CX1045]	
CAT93HC46(08bit)(K)@SOIC8 [CX1044]	
CAT93HC46(08bit)(S)@SOIC8 [CX1045]	
CAT93HC46(08bit)(U)@TSSOP8 [CX1059]	
CAT93HC46(16bit) [CX0001]	
CAT93HC46(16bit)(J)@SOIC8 [CX1045]	
CAT93HC46(16bit)(K)@SOIC8 [CX1044]	
CAT93HC46(16bit)(S)@SOIC8 [CX1045]	
CAT93HC46(16bit)(U)@TSSOP8 [CX1059]	

#### DRAM & SRAM

CAT71C256 [CX0001]	CAT71C256@TSOP28 [CX1001]
CAT71C256L [CX0001]	CAT71C256L@TSOP28 [CX1001]

## E (E) PROM/FRAM/NVRAM

MC24LC02 [CX0001]	MC24LC02@SOP8 [CX1045]
MC24LC02@TSSOP8 [CX1059]	MC24LC04 [CX0001]
MC24LC04@SOP8 [CX1045]	MC24LC04@TSSOP8 [CX1059]
MC24LC08 [CX0001]	MC24LC08@SOP8 [CX1045]
MC24LC08@TSSOP8 [CX1059]	MC24LC16 [CX0001]
MC24LC16@SOP8 [CX1045]	MC24LC16@TSSOP8 [CX1059]

## CERAMATE

### E (E) PROM/FRAM/NVRAM

24LC02 [CX0001]	24LC02@SOIC8 [CX1045]
24LC02@TSSOP8 [CX1059]	24LC08 [CX0001]
24LC08@SOIC8 [CX1045]	24LC08@TSSOP8 [CX1059]
24LC16 [CX0001]	24LC16@SOIC8 [CX1045]
24LC16@TSSOP8 [CX1059]	24LLC02 [CX0001]
24LLC02@SOIC8 [CX1045]	24LLC02@TSSOP8 [CX1059]
24LLC08 [CX0001]	24LLC08@SOIC8 [CX1045]
24LLC08@TSSOP8 [CX1059]	93LC46 [CX0001]
93LC46@SOIC8 [CX1045]	93LC46R [CX0001]
93LC46R@SOIC8 [CX1045]	93LC56 [CX0001]
93LC56@SOIC8 [CX1045]	93LC66 [CX0001]
93LC66@SOIC8 [CX1045]	

## CETC58

### PLD

JGAL16V8B [CX0001]	JGAL20V8B [CX0001]
JGAL22V10D [CX0001]	

## CFEON

### E (E) PROM/FRAM/NVRAM

EN25F16 [CX0001]	EN25F16@SOP16 [CX1033#1]
EN25F16@SOP8 [CX1044#1]	EN25F16@VDFN8 [CX4005#1]
EN25F80 [CX0001]	EN25F80@SOP8 [CX1044#1]
EN25F80@VDFN8 [CX4005#1]	EN25Q128@BGA24 [CX5146]
EN25Q128@SOP16 [CX1033#1]	EN25Q128@VDFN8 [CX4006#1]
EN25QA128@BGA24 [CX5146]	EN25QA128@SOP16 [CX1033#1]
EN25QA128@SOP8 [CX1044#1]	EN25QA256@BGA24 [CX5146]
EN25QA32 [CX0001]	EN25QA32@SOP8 [CX1044#1]
EN25QA32@VDFN8 [CX4005#1]	EN25QA64-B24 [CX5146]
EN25QA64-S8 [CX1044#1]	EN25QH16 [CX0001]
EN25QH16@SOP8(150 mil) [CX1045#1]	
EN25QH16@SOP8(200 mil) [CX1044#1]	
EN25QH16@TFBGA24 [CX5146]	EN25QH16@VDFN8 [CX4006#1]
EN25QH256@SOP16 [CX1033#1]	EN25QH256@TFBGA24 [CX5146]
EN25QH256@VDFN8 [CX4006#1]	EN25QH32 [CX0001]
EN25QH32@SOP8 [CX1044#1]	EN25QH32@TFBGA24 [CX5146]
EN25QH32@VDFN8 [CX4005#1]	EN25QH64 [CX0001]
EN25QH64@SOP8 [CX1044#1]	EN25QH64@TFBGA24 [CX5146]
EN25QH64@VDFN8 [CX4005#1]	EN25T16@SOP8 [CX1044#1]

EN25T16@VDFN8 [CX4005#1]  
EN25T80@SOP8 [CX1044#1]  
EN29F002AB [CX0001]  
EN29F002AB@TSOP32 [CX1002]  
EN29F002ANB@PLCC32 [CX2032]  
EN29F002ANT [CX0001]  
EN29F002ANT@TSOP32 [CX1002]  
EN29F002AT@PLCC32 [CX2032]  
EN29F002B [CX0001]  
EN29F002B@TSOP32 [CX1002]  
EN29F002NB@PLCC32 [CX2032]  
EN29F002NT [CX0001]  
EN29F002NT@TSOP32 [CX1002]  
EN29F002T@PLCC32 [CX2032]  
EN29F010 [CX0001]  
EN29F010@TSOP32 [CX1002]  
EN29F040 [CX0001]  
EN29F040@TSOP32 [CX1002]  
EN29F040A@PLCC32 [CX2032]  
EN29F080@TSOP40 [CX1006]  
EN29F512@PLCC32 [CX2032]  
EN29F512@VSOP32 [CX1003]  
EN29F800T@TSOP48 [CX1004]  
EN29GA128L@FBGA64 [CX5074]  
EN29GA256L@FBGA64 [CX5074]  
EN29GL064AB@TSOP48 [CX1004]  
EN29GL064AT@TSOP48 [CX1004]  
EN29GL064B@TSOP48 [CX1004]  
EN29GL064H@TSOP56 [CX1011]  
EN29GL064L@TSOP56 [CX1011]  
EN29GL064T@TSOP48 [CX1004]  
EN29GL128H@TSOP56 [CX1011]  
EN29GL128L@TSOP56 [CX1011]  
EN29LV010@TSOP32 [CX1002]  
EN29LV010@WFBGA34 [CX5037]  
EN29LV040@TSOP32 [CX1002]  
EN29LV040A [CX0001]  
EN29LV040A@TSOP32 [CX1002]  
EN29LV160AB@FBGA48 [CX5002]  
EN29LV160AT@FBGA48 [CX5002]  
EN29LV160B@FBGA48 [CX5002]  
EN29LV160BB@FBGA48 [CX5002]  
EN29LV160BB@TSOP48(slow) [CX1004]  
EN29LV160BT@FBGA48 [CX5002]  
EN29LV160BT@TSOP48(slow) [CX1004]  
EN29LV160CB@FBGA48 [CX5002]  
EN29LV160CT@FBGA48 [CX5002]  
EN29LV160T@FBGA48 [CX5002]  
EN29LV320AB@FBGA48 [CX5002]  
EN29LV320AT@FBGA48 [CX5002]  
EN29LV320B@FBGA48 [CX5002]  
EN29LV320BB@FBGA48 [CX5002]  
EN29LV320BT@FBGA48 [CX5002]  
EN29LV320CB@FBGA48 [CX5002]  
EN29LV320CT@FBGA48 [CX5002]  
EN29LV320T@FBGA48 [CX5002]  
EN29LV400AB@FBGA48 [CX5002]  
EN29LV400AT@FBGA48 [CX5002]  
EN29LV400B@FBGA48 [CX5002]  
EN25T80 [CX0001]  
EN25T80@VDFN8 [CX4005#1]  
EN29F002AB@PLCC32 [CX2032]  
EN29F002ANB [CX0001]  
EN29F002ANB@TSOP32 [CX1002]  
EN29F002ANT@PLCC32 [CX2032]  
EN29F002AT [CX0001]  
EN29F002AT@TSOP32 [CX1002]  
EN29F002B@PLCC32 [CX2032]  
EN29F002NB [CX0001]  
EN29F002NB@TSOP32 [CX1002]  
EN29F002NT@PLCC32 [CX2032]  
EN29F002T [CX0001]  
EN29F002T@TSOP32 [CX1002]  
EN29F010@PLCC32 [CX2032]  
EN29F010@VSOP32 [CX1003]  
EN29F040@PLCC32 [CX2032]  
EN29F040A [CX0001]  
EN29F040A@TSOP32 [CX1002]  
EN29F512 [CX0001]  
EN29F512@TSOP32 [CX1002]  
EN29F800B@TSOP48 [CX1004]  
EN29GA128H@FBGA64 [CX5074]  
EN29GA256H@FBGA64 [CX5074]  
EN29GL064AB@FBGA48 [CX5002]  
EN29GL064AT@FBGA48 [CX5002]  
EN29GL064B@FBGA48 [CX5002]  
EN29GL064H@FBGA64 [CX5074]  
EN29GL064L@FBGA64 [CX5074]  
EN29GL064T@FBGA48 [CX5002]  
EN29GL128H@FBGA64 [CX5074]  
EN29GL128L@FBGA64 [CX5074]  
EN29LV010@PLCC32 [CX2032]  
EN29LV010@VSOP32 [CX1003]  
EN29LV040@PLCC32 [CX2032]  
EN29LV040@VSOP32 [CX1003]  
EN29LV040A@PLCC32 [CX2032]  
EN29LV040A@VSOP32 [CX1003]  
EN29LV160AB@TSOP48 [CX1004]  
EN29LV160AT@TSOP48 [CX1004]  
EN29LV160B@TSOP48 [CX1004]  
EN29LV160BB@TSOP48 [CX1004]  
EN29LV160BT@TSOP48 [CX1004]  
EN29LV160CB@TSOP48 [CX1004]  
EN29LV160CT@TSOP48 [CX1004]  
EN29LV160T@TSOP48 [CX1004]  
EN29LV320AB@TSOP48 [CX1004]  
EN29LV320AT@TSOP48 [CX1004]  
EN29LV320B@TSOP48 [CX1004]  
EN29LV320BB@TSOP48 [CX1004]  
EN29LV320BT@TSOP48 [CX1004]  
EN29LV320CB@TSOP48 [CX1004]  
EN29LV320CT@TSOP48 [CX1004]  
EN29LV320T@TSOP48 [CX1004]  
EN29LV400AB@TSOP48 [CX1004]  
EN29LV400AT@TSOP48 [CX1004]  
EN29LV400B@TSOP48 [CX1004]

EN29LV400T@FBGA48 [CX5002]  
EN29LV512@PLCC32 [CX2032]  
EN29LV512@VSOP32 [CX1003]  
EN29LV640AB@TSOP48 [CX1004]  
EN29LV640AT@TSOP48 [CX1004]  
EN29LV640B@TSOP48 [CX1004]  
EN29LV640H@TSOP48 [CX1004]  
EN29LV640L@TSOP48 [CX1004]  
EN29LV640T@TSOP48 [CX1004]  
EN29LV641H@TSOP48 [CX1004]  
EN29LV641L@TSOP48 [CX1004]  
EN29LV800AB@TSOP48 [CX1004]  
EN29LV800AT@TSOP48 [CX1004]  
EN29LV800B@TSOP48 [CX1004]  
EN29LV800BB@FBGA48 [CX5002]  
EN29LV800BT@FBGA48 [CX5002]  
EN29LV800CB@FBGA48 [CX5002]  
EN29LV800CT@FBGA48 [CX5002]  
EN29LV800T@TSOP48 [CX1004]  
EN29PL032@FBGA48 [CX5002]  
EN29PL032@TSOP48 [CX1004]  
EN29PL064@FBGA48 [CX5002]  
EN29PL064@TSOP48 [CX1004]  
EN29SL160B@TSOP48 [CX1004]  
EN29SL160B@WLGA48 [CX5038]  
EN29SL160T@TSOP48 [CX1004]  
EN29SL160T@WLGA48 [CX5038]  
EN29SL400B@TSOP48 [CX1004]  
EN29SL400T@TSOP48 [CX1004]  
EN29SL800B@TSOP48 [CX1004]  
EN29SL800B@WLGA48 [CX5038]  
EN29SL800T@TSOP48 [CX1004]  
EN29SL800T@WLGA48 [CX5038]  
EN39LV010@VSOP32 [CX1003]  
EN39SL160H@FBGA48 [CX5002]  
EN39SL160L@FBGA48 [CX5002]  
EN39SL800@FBGA48 [CX5002]  
EN39SL800@WFBGA48 [CX5037]  
EN39SL801@WFBGA48 [CX5037]  
EN71GL032A0@FBGA56 [CX5045]  
EN71GL064B0@FBGA56 (XW) [CX5005]  
EN71GL128B0@FBGA56 (XW) [CX5005]  
EN71NS064B0@FBGA56 [CX5094]  
EN71NS128C0@FBGA56 [CX5094]  
EN71PL032A0@FBGA56 [CX5045]  
EN71PL032A0A@FBGA56 [CX5045]  
EN71PL064B0@FBGA56 [CX5045]  
EN29LV400T@TSOP48 [CX1004]  
EN29LV512@TSOP32 [CX1002]  
EN29LV640AB@FBGA48 [CX5002]  
EN29LV640AT@FBGA48 [CX5002]  
EN29LV640B@FBGA48 [CX5002]  
EN29LV640H@FBGA48 [CX5002]  
EN29LV640L@FBGA48 [CX5002]  
EN29LV640T@FBGA48 [CX5002]  
EN29LV641H@FBGA63 [CX5041]  
EN29LV641L@FBGA63 [CX5041]  
EN29LV800AB@FBGA48 [CX5002]  
EN29LV800AT@FBGA48 [CX5002]  
EN29LV800B@TSOP48 [CX1004]  
EN29LV800BB@TSOP48 [CX1004]  
EN29LV800BT@TSOP48 [CX1004]  
EN29LV800CB@TSOP48 [CX1004]  
EN29LV800CT@TSOP48 [CX1004]  
EN29NS064@FBGA56 [CX5094]  
EN29PL032@FBGA56 [CX5045]  
EN29PL032A@TSOP48 [CX1004]  
EN29PL064@FBGA56 [CX5045]  
EN29SL160B@FBGA48 [CX5002]  
EN29SL160B@WFBGA48 [CX5038]  
EN29SL160T@FBGA48 [CX5002]  
EN29SL160T@WFBGA48 [CX5038]  
EN29SL400B@FBGA48 [CX5002]  
EN29SL400T@FBGA48 [CX5002]  
EN29SL800B@FBGA48 [CX5002]  
EN29SL800B@WFBGA48 [CX5038]  
EN29SL800T@FBGA48 [CX5002]  
EN29SL800T@WFBGA48 [CX5038]  
EN39LV010@PLCC32 [CX2032]  
EN39LV010@WFBGA34 [CX5037]  
EN39SL160H@WFBGA48 [CX5037]  
EN39SL160L@WFBGA48 [CX5037]  
EN39SL800@TSOP48 [CX1043]  
EN39SL801@FBGA48 [CX5002]  
EN71GL03280@FBGA56 [CX5045]  
EN71GL064B0@FBGA56 [CX5045]  
EN71GL128B0@FBGA56 [CX5045]  
EN71NS032A0@FBGA56 [CX5094]  
EN71NS128B0@FBGA56 [CX5094]  
EN71PL03280@FBGA56 [CX5045]  
EN71PL032A0@FBGA56 (XW) [CX5005]  
EN71PL064A0@FBGA56 [CX5045]

## CHINA CORE

### MICROCONTROLLER

CCM89C51 [CX0001]  
CCM89C51@TQFP44 [CX3003]  
CCM89C52@PLCC44 [CX2044]  
CCM89C51@PLCC44 [CX2044]  
CCM89C52 [CX0001]  
CCM89C52@TQFP44 [CX3003]

## CHINGIS

## E (E) PROM/FRAM/NVRAM

PM25LD010@SOP8 [CX1045#1]	PM25LD010@TSSOP8 [CX1059#3]
PM25LD010@WSON8 [CX4005#1]	PM25LD010C@SOP8 [CX1045#1]
PM25LD010C@SOP8(SG) [CX1045#1]	PM25LD010C@TSSOP8 [CX1059#3]
PM25LD010C@TSSOP8(SG) [CX1059#1]	PM25LD010C@WSON8 [CX4005#1]
PM25LD010C@WSON8(SG) [CX4005#1]	PM25LD020@SOP8 [CX1045#1]
PM25LD020@TSSOP8 [CX1059#3]	PM25LD020@WSON8 [CX4005#1]
PM25LD020C@SOP8 [CX1045#1]	PM25LD020C@SOP8(SG) [CX1045#1]
PM25LD020C@TSSOP8 [CX1059#3]	PM25LD020C@TSSOP8(SG) [CX1059#1]
PM25LD020C@WSON8 [CX4005#1]	PM25LD020C@WSON8(SG) [CX4005#1]
PM25LD040(B)@SOIC8 [CX1044#1]	PM25LD040(Q)@WSON8 [CX4005#1]
PM25LD040(S)@SOIC8 [CX1045#1]	PM25LD256C@SOP8 [CX1045#1]
PM25LD256C@TSSOP8 [CX1059#3]	PM25LD256C@WSON8 [CX4005#1]
PM25LD512@SOP8 [CX1045#1]	PM25LD512@TSSOP8 [CX1059#3]
PM25LD512@WSON8 [CX4005#1]	PM25LD512C@SOP8 [CX1045#1]
PM25LD512C@TSSOP8 [CX1059#3]	PM25LD512C@WSON8 [CX4005#1]
PM25LV010(B)@SOIC8 [CX1044]	PM25LV010(Q)@WSON8 [CX4005]
PM25LV010(S)@SOIC8 [CX1045]	PM25LV020(B)@SOIC8 [CX1044#1]
PM25LV020(Q)@WSON8 [CX4005#1]	PM25LV020(S)@SOIC8 [CX1045#1]
PM25LV040(B)@SOIC8 [CX1044#1]	PM25LV040(Q)@WSON8 [CX4005#1]
PM25LV040(S)@SOIC8 [CX1045#1]	PM25LV512(B)@SOIC8 [CX1044]
PM25LV512(Q)@WSON8 [CX4005]	PM25LV512(S)@SOIC8 [CX1045]
PM25W020(B)@SOIC8 [CX1044#1]	PM25W020(Q)@WSON8 [CX4005#1]
PM25W020(S)@SOIC8 [CX1045#1]	PM29F002B [CX0001]
PM29F002B@PLCC32 [CX2032]	PM29F002T [CX0001]
PM29F002T@PLCC32 [CX2032]	PM29F004B [CX0001]
PM29F004B@PLCC32 [CX2032]	PM29F004T [CX0001]
PM29F004T@PLCC32 [CX2032]	PM29LV002B [CX0001]
PM29LV002B@PLCC32 [CX2032]	PM29LV002B@VSOP32 [CX1003]
PM29LV002T [CX0001]	PM29LV002T@PLCC32 [CX2032]
PM29LV002T@VSOP32 [CX1003]	PM29LV004B@PLCC32 [CX2032]
PM29LV004B@VSOP32 [CX1003]	PM29LV004T@PLCC32 [CX2032]
PM29LV004T@VSOP32 [CX1003]	PM29LV104RB@PLCC32 [CX2032]
PM29LV104RB@VSOP32 [CX1003]	PM29LV104RT@PLCC32 [CX2032]
PM29LV104RT@VSOP32 [CX1003]	PM37LV512 [CX0001]
PM37LV512@PLCC32 [CX2032]	PM37LV512@VSOP32 [CX1003]
PM39F010 [CX0001]	PM39F010@PLCC32 [CX2032]
PM39F010@VSOP32 [CX1003]	PM39F020 [CX0001]
PM39F020@PLCC32 [CX2032]	PM39F020@VSOP32 [CX1003]
PM39F040 [CX0001]	PM39F040@PLCC32 [CX2032]
PM39F040@VSOP32 [CX1003]	PM39LV010@PLCC32 [CX2032]
PM39LV010@VSOP32 [CX1003]	PM39LV010R@PLCC32 [CX2032]
PM39LV010R@VSOP32 [CX1003]	PM39LV020@PLCC32 [CX2032]
PM39LV020@VSOP32 [CX1003]	PM39LV040@PLCC32 [CX2032]
PM39LV040@VSOP32 [CX1003]	PM39LV512@PLCC32 [CX2032]
PM39LV512@VSOP32 [CX1003]	PM39LV512R@PLCC32 [CX2032]
PM39LV512R@VSOP32 [CX1003]	PM49FL002T@PLCC32 [CX2032]
PM49FL002T@VSOP32 [CX1003]	PM49FL004T@PLCC32 [CX2032]
PM49FL004T@VSOP32 [CX1003]	PM49FL008T@PLCC32 [CX2032]
PM49FL008T@VSOP32 [CX1003]	PM49LP002T@PLCC32 [CX2032]
PM49LP002T@VSOP32 [CX1003]	

## CHIPCON

### MICROCONTROLLER

CC1010@TQFP64 [CX3011]

CC1110F08@QLP36 [CX4021]

CC1110F16@QLP36 [CX4021]  
CC2430F128@QLP48 [CX4021]  
CC2430F64@QLP48 [CX4021]  
CC2431F32@QLP48 [CX4021]  
CC2510F08@QLP36 [CX4021]  
CC2510F32@QLP36 [CX4021]  
CC2511F16@QLP36 [CX4021]

CC1110F32@QLP36 [CX4021]  
CC2430F32@QLP48 [CX4021]  
CC2431F128@QLP48 [CX4021]  
CC2431F64@QLP48 [CX4021]  
CC2510F16@QLP36 [CX4021]  
CC2511F08@QLP36 [CX4021]  
CC2511F32@QLP36 [CX4021]

## CHIPMAST

### MICROCONTROLLER

M151-S1@SOP16 [CX1016]  
M152-S2@SOP16 [CX1016]

M151-S2@SOP16 [CX1016]

## CHIPON

### MICROCONTROLLER

C61F120 [CX0001]  
C61F120@SOIC8 [CX1032]  
C61F121 [CX0001]  
C61F121@TSSOP14 [CX1000]  
C61F132@QFN8 [CX4005]  
C61F132@SSOP20 [CX1026]  
C61F133 [CX0001]  
C61F133@TSSOP14 [CX1000]  
C61F182@QFN28 [CX4014]  
C61F182@SSOP28 [CX1026]  
C61F183@QFN28 [CX4014]  
C61F183@SSOP28 [CX1026]  
C61F184@QFN44 [CX4018]  
C61F186 [CX0001]  
C61F186@SOIC28 [CX1033]  
C61F187 [CX0001]  
C61F187@QFP44 [CX3003]  
C61F21@QFN8 [CX4004]  
C61F21@SSOP8 [CX1016]  
C61F23@QFN16 [CX4010]  
C61F23@TSSOP14 [CX1000]

C61F120@QFN8 [CX4005]  
C61F120@SSOP8 [CX1016]  
C61F121@SOIC14 [CX1030]  
C61F132 [CX0001]  
C61F132@SOIC8 [CX1032]  
C61F132@SSOP8 [CX1016]  
C61F133@SOIC14 [CX1030]  
C61F182 [CX0001]  
C61F182@SOIC28 [CX1033]  
C61F183 [CX0001]  
C61F183@SOIC28 [CX1033]  
C61F184 [CX0001]  
C61F184@QFP44 [CX3003]  
C61F186@QFN28 [CX4014]  
C61F186@SSOP28 [CX1026]  
C61F187@QFN44 [CX4018]  
C61F21 [CX0001]  
C61F21@SOIC8 [CX1032]  
C61F23 [CX0001]  
C61F23@SOIC14 [CX1030]

## CHIPSWINNER

### E (E) PROM/FRAM/NVRAM

CW24C02 [CX0001]  
CW24C02@SOP8 [CX1045]  
CW24C02@TSOT23-5 [CX1041]  
CW24C02B [CX0001]  
CW24C02B@SOP8 [CX1045]  
CW24C02B@TSOT23-5 [CX1041]  
CW24C02C [CX0001]  
CW24C02C@SOP8 [CX1045]  
CW24C02C@TSOT23-5 [CX1041]  
CW24C04 [CX0001]  
CW24C04@SOP8 [CX1045]

CW24C02@DFN8 [CX4002]  
CW24C02@SOT23-5 [CX1041]  
CW24C02@TSSOP8 [CX1059]  
CW24C02B@DFN8 [CX4002]  
CW24C02B@SOT23-5 [CX1041]  
CW24C02B@TSSOP8 [CX1059]  
CW24C02C@DFN8 [CX4002]  
CW24C02C@SOT23-5 [CX1041]  
CW24C02C@TSSOP8 [CX1059]  
CW24C04@DFN8 [CX4002]  
CW24C04@SOT23-5 [CX1041]



CW24C04@TSOT23-5 [CX1041]  
CW24C04A [CX0001]  
CW24C04A@SOP8 [CX1045]  
CW24C04A@TSOT23-5 [CX1041]  
CW24C08 [CX0001]  
CW24C08@SOP8 [CX1045]  
CW24C08@TSOT23-5 [CX1041]  
CW24C08B [CX0001]  
CW24C08B@SOP8 [CX1045]  
CW24C08B@TSOT23-5 [CX1041]  
CW24C08C [CX0001]  
CW24C08C@SOP8 [CX1045]  
CW24C08C@TSOT23-5 [CX1041]  
CW24C128 [CX0001]  
CW24C128@SOP8 [CX1045]  
CW24C16 [CX0001]  
CW24C16@SOP8 [CX1045]  
CW24C16@TSOT23-5 [CX1041]  
CW24C16A [CX0001]  
CW24C16A@SOP8 [CX1045]  
CW24C16A@TSOT23-5 [CX1041]  
CW24C256 [CX0001]  
CW24C256@SOP8 [CX1045]  
CW24C32 [CX0001]  
CW24C32@SOP8 [CX1045]  
CW24C64 [CX0001]  
CW24C64@SOP8 [CX1045]  
CW25P01@SOP8 [CX1045]  
CW25P05@SOP8 [CX1045]

CW24C04@TSSOP8 [CX1059]  
CW24C04A@DFN8 [CX4002]  
CW24C04A@SOT23-5 [CX1041]  
CW24C04A@TSSOP8 [CX1059]  
CW24C08@DFN8 [CX4002]  
CW24C08@SOT23-5 [CX1041]  
CW24C08@TSSOP8 [CX1059]  
CW24C08B@DFN8 [CX4002]  
CW24C08B@SOT23-5 [CX1041]  
CW24C08B@TSSOP8 [CX1059]  
CW24C08C@DFN8 [CX4002]  
CW24C08C@SOT23-5 [CX1041]  
CW24C08C@TSSOP8 [CX1059]  
CW24C128@DFN8 [CX4002]  
CW24C128@TSSOP8 [CX1059]  
CW24C16@DFN8 [CX4002]  
CW24C16@SOT23-5 [CX1041]  
CW24C16@TSSOP8 [CX1059]  
CW24C16A@DFN8 [CX4002]  
CW24C16A@SOT23-5 [CX1041]  
CW24C16A@TSSOP8 [CX1059]  
CW24C256@DFN8 [CX4002]  
CW24C256@TSSOP8 [CX1059]  
CW24C32@DFN8 [CX4002]  
CW24C32@TSSOP8 [CX1059]  
CW24C64@DFN8 [CX4002]  
CW24C64@TSSOP8 [CX1059]  
CW25P02@SOP8 [CX1045]  
CW25P10@SOP8 [CX1045]

## MICROCONTROLLER

CW89F51 [CX0001]  
CW89F51@TQFP44 [CX3002]  
CW89F52@PLCC44 [CX2044]  
CW89F54 [CX0001]  
CW89F54@TQFP44 [CX3002]

CW89F51@PLCC44 [CX2044]  
CW89F52 [CX0001]  
CW89F52@TQFP44 [CX3002]  
CW89F54@PLCC44 [CX2044]

## CKD Technology

### E (E) PROM/FRAM/NVRAM

CKD24A02 [CX0001]

CKD24A02@SOP8 [CX1045]

## CORERIVER

### E (E) PROM/FRAM/NVRAM

CR24C01 [CX0001]  
CR24C01@TDFN8 [CX4002]  
CR24C02 [CX0001]  
CR24C02@TDFN8 [CX4002]  
CR24C04 [CX0001]  
CR24C04@TDFN8 [CX4002]  
CR24C08 [CX0001]  
CR24C08@TDFN8 [CX4002]

CR24C01@SOIC8 [CX1045]  
CR24C01@TSSOP8 [CX1059]  
CR24C02@SOIC8 [CX1045]  
CR24C02@TSSOP8 [CX1059]  
CR24C04@SOIC8 [CX1045]  
CR24C04@TSSOP8 [CX1059]  
CR24C08@SOIC8 [CX1045]  
CR24C08@TSSOP8 [CX1059]

CR24C128 [CX0001]  
CR24C128@TSSOP8 [CX1059]  
CR24C16@SOIC8 [CX1045]  
CR24C16@TSSOP8 [CX1059]  
CR24C256@SOIC8 [CX1045]  
CR24C32 [CX0001]  
CR24C32@TSSOP8 [CX1059]  
CR24C64@SOIC8 [CX1045]

CR24C128@SOIC8 [CX1045]  
CR24C16 [CX0001]  
CR24C16@TDFN8 [CX4002]  
CR24C256 [CX0001]  
CR24C256@TSSOP8 [CX1059]  
CR24C32@SOIC8 [CX1045]  
CR24C64 [CX0001]  
CR24C64@TSSOP8 [CX1059]

## MICROCONTROLLER

GC87C520A0 [CX0001]  
GC87C520A0@PLCC44 [CX2044]  
GC89L541A0@MLF32 [CX4015]  
GC89L541A0@PQFP44 [CX3066]  
GC89L581A0@LQFP44 [CX3002]  
GC89L581A0@MQFP44 [CX3066]  
GC89L581A0@QFN32 [CX4015]  
GC89L591A0@MLF32 [CX4015]  
GC89L591A0@PQFP44 [CX3066]  
TouchCore32H@MLF24 [CX4012]

GC87C520A0@MQFP44 [CX3002]  
GC89L541A0@LQFP44 [CX3002]  
GC89L541A0@MQFP44 [CX3066]  
GC89L541A0@QFN32 [CX4015]  
GC89L581A0@MLF32 [CX4015]  
GC89L581A0@PQFP44 [CX3066]  
GC89L591A0@LQFP44 [CX3002]  
GC89L591A0@MQFP44 [CX3066]  
GC89L591A0@QFN32 [CX4015]

## CUSTOMER

### E (E) PROM/FRAM/NVRAM

M27C256B [CX0001]

## CWI

### E (E) PROM/FRAM/NVRAM

39LV040@VSOP32 [CX1003]

## CYGNAL

### MICROCONTROLLER

C8051F000@TQFP64 [CX3011]  
C8051F002@TQFP32 [CX3001]  
C8051F006@TQFP48 [CX3007]  
C8051F010@TQFP64 [CX3011]  
C8051F012@TQFP32 [CX3001]  
C8051F016@TQFP48 [CX3007]  
C8051F018@TQFP64  
C8051F020@TQFP100 [CX3021]  
C8051F021@TQFP64 [CX3011]  
C8051F022@TQFP100 [CX3021]  
C8051F023@TQFP64 [CX3011]  
C8051F040@TQFP100 [CX3021]  
C8051F041@TQFP64 [CX3011]  
C8051F042@TQFP100 [CX3021]  
C8051F043@TQFP64 [CX3011]  
C8051F044@TQFP100 [CX3021]  
C8051F045@TQFP64 [CX3011]

C8051F001@TQFP48 [CX3007]  
C8051F005@TQFP64 [CX3011]  
C8051F007@TQFP32 [CX3001]  
C8051F011@TQFP48 [CX3007]  
C8051F015@TQFP64 [CX3011]  
C8051F017@TQFP32 [CX3001]  
C8051F019@TQFP48  
C8051F020JTAG [CX0001]  
C8051F021JTAG [CX0001]  
C8051F022JTAG [CX0001]  
C8051F023JTAG [CX0001]  
C8051F040JTAG [CX0001]  
C8051F041JTAG [CX0001]  
C8051F042JTAG [CX0001]  
C8051F043JTAG [CX0001]  
C8051F044JTAG [CX0001]  
C8051F045JTAG [CX0001]

C8051F046@TQFP100 [CX3021]                   C8051F046JTAG [CX0001]  
C8051F047@TQFP64 [CX3011]                   C8051F047JTAG [CX0001]  
C8051F060@TQFP100 [CX3021]                   C8051F061@TQFP64 [CX3011]  
C8051F062@TQFP100 [CX3021]                   C8051F063@TQFP64 [CX3011]  
C8051F064@TQFP100 [CX3021]                   C8051F065@TQFP64 [CX3011]  
C8051F066@TQFP100 [CX3021]                   C8051F067@TQFP64 [CX3011]  
C8051F120\*ISP [CX0001]                   C8051F120@TQFP100 [CX3021]  
C8051F120-GQ\*ISP [CX0001]                   C8051F120-GQ@TQFP100 [CX3021]  
C8051F121\*ISP [CX0001]                   C8051F121@TQFP64 [CX3011]  
C8051F121-GQ\*ISP [CX0001]                   C8051F121-GQ@TQFP64 [CX3011]  
C8051F122\*ISP [CX0001]                   C8051F122@TQFP100 [CX3021]  
C8051F122-GQ\*ISP [CX0001]                   C8051F122-GQ@TQFP100 [CX3021]  
C8051F123\*ISP [CX0001]                   C8051F123@TQFP64 [CX3011]  
C8051F123-GQ\*ISP [CX0001]                   C8051F123-GQ@TQFP64 [CX3011]  
C8051F124\*ISP [CX0001]                   C8051F124@TQFP100 [CX3021]  
C8051F124-GQ\*ISP [CX0001]                   C8051F124-GQ@TQFP100 [CX3021]  
C8051F125\*ISP [CX0001]                   C8051F125@TQFP64 [CX3011]  
C8051F125-GQ\*ISP [CX0001]                   C8051F125-GQ@TQFP64 [CX3011]  
C8051F126\*ISP [CX0001]                   C8051F126@TQFP100 [CX3021]  
C8051F126-GQ\*ISP [CX0001]                   C8051F126-GQ@TQFP100 [CX3021]  
C8051F127\*ISP [CX0001]                   C8051F127@TQFP64 [CX3011]  
C8051F127-GQ\*ISP [CX0001]                   C8051F127-GQ@TQFP64 [CX3011]  
C8051F130\*ISP [CX0001]                   C8051F130@TQFP100 [CX3021]  
C8051F130-GQ\*ISP [CX0001]                   C8051F130-GQ@TQFP100 [CX3021]  
C8051F131\*ISP [CX0001]                   C8051F131@TQFP64 [CX3011]  
C8051F131-GQ\*ISP [CX0001]                   C8051F131-GQ@TQFP64 [CX3011]  
C8051F132\*ISP [CX0001]                   C8051F132@TQFP100 [CX3021]  
C8051F132-GQ\*ISP [CX0001]                   C8051F132-GQ@TQFP100 [CX3021]  
C8051F133\*ISP [CX0001]                   C8051F133@TQFP64 [CX3011]  
C8051F133-GQ\*ISP [CX0001]                   C8051F133-GQ@TQFP64 [CX3011]  
C8051F206@TQFP48 [CX3007]                   C8051F220@TQFP48 [CX3007]  
C8051F221@TQFP32 [CX3001]                   C8051F226@TQFP48 [CX3007]  
C8051F230@TQFP48 [CX3007]                   C8051F231@TQFP32 [CX3001]  
C8051F236@TQFP48 [CX3007]                   C8051F300@QFN11 [CX4007]  
C8051F300-GM@QFN11 [CX4007]                   C8051F300-GS [CX1016]  
C8051F301@QFN11 [CX4007]                   C8051F301-GM@QFN11 [CX4007]  
C8051F301-GS [CX1016]                   C8051F302@QFN11 [CX4007]  
C8051F302-GM@QFN11 [CX4007]                   C8051F302-GS [CX1016]  
C8051F303@QFN11 [CX4007]                   C8051F303-GM@QFN11 [CX4007]  
C8051F303-GS [CX1016]                   C8051F304@QFN11 [CX4007]  
C8051F304-GM@QFN11 [CX4007]                   C8051F304-GS [CX1016]  
C8051F305@QFN11 [CX4007]                   C8051F305-GM@QFN11 [CX4007]  
C8051F305-GS [CX1016]                   C8051F310@TQFP32 [CX3001]  
C8051F310A@TQFP32 [CX3001]                   C8051F310A-GQ@TQFP32 [CX3001]  
C8051F310-GQ@TQFP32 [CX3001]                   C8051F311@QFN28 [CX4013]  
C8051F311-GM@QFN28 [CX4013]                   C8051F312@TQFP32 [CX3001]  
C8051F312-GQ@TQFP32 [CX3001]                   C8051F313@QFN28 [CX4013]  
C8051F313-GM@QFN28 [CX4013]                   C8051F314@TQFP32 [CX3001]  
C8051F314-GQ@TQFP32 [CX3001]                   C8051F315@QFN28 [CX4013]  
C8051F315-GM@QFN28 [CX4013]                   C8051F316-GM@QFN24 [CX4012]  
C8051F317-GM@QFN24 [CX4012]                   C8051F320@TQFP32 [CX3001]  
C8051F320A@TQFP32 [CX3001]                   C8051F320A-GQ@TQFP32 [CX3001]  
C8051F320-GQ@TQFP32 [CX3001]                   C8051F321@QFN28 [CX4013]  
C8051F321@QFN28(Left Down) [CX4013]  
C8051F321A@QFN28 [CX4013]  
C8051F321A@QFN28(Left Down) [CX4013]  
C8051F321A-GM@QFN28 [CX4013]  
C8051F321A-GM@QFN28(Left Down) [CX4013]  
C8051F321-GM@QFN28 [CX4013]

C8051F321-GM@QFN28(Left Down) [CX4013]  
C8051F326@QFN28 [CX4013] C8051F326-GM@QFN28 [CX4013]  
C8051F326-GQ@QFN28 [CX4013] C8051F327@QFN28 [CX4013]  
C8051F327-GM@QFN28 [CX4013] C8051F327-GQ@QFN28 [CX4013]  
C8051F330@MLP20 [CX4011] C8051F330D [CX0001]  
C8051F330-GM@MLP20 [CX4011] C8051F330-GP [CX0001]  
C8051F331@MLP20 [CX4011] C8051F331-GM@MLP20 [CX4011]  
C8051F332@MLP20 [CX4011] C8051F332-GM@MLP20 [CX4011]  
C8051F333@MLP20 [CX4011] C8051F333-GM@MLP20 [CX4011]  
C8051F334@MLP20 [CX4011] C8051F334-GM@MLP20 [CX4011]  
C8051F335@MLP20 [CX4011] C8051F335-GM@MLP20 [CX4011]  
C8051F336@MLP20 [CX4011] C8051F336-GM@MLP20 [CX4011]  
C8051F337@MLP20 [CX4011] C8051F337-GM@MLP20 [CX4011]  
C8051F338@MLP24 [CX4012] C8051F338-GM@MLP24 [CX4012]  
C8051F339@MLP24 [CX4012] C8051F339-GM@MLP24 [CX4012]  
C8051F340@TQFP48 [CX3007] C8051F340-GQ@TQFP48 [CX3007]  
C8051F341@TQFP48 [CX3007] C8051F341-GQ@TQFP48 [CX3007]  
C8051F342@LQFP32 [CX3001] C8051F342-GQ@LQFP32 [CX3001]  
C8051F343@LQFP32 [CX3001] C8051F343-GQ@LQFP32 [CX3001]  
C8051F344@TQFP48 [CX3007] C8051F344-GQ@TQFP48 [CX3007]  
C8051F345@TQFP48 [CX3007] C8051F345-GQ@TQFP48 [CX3007]  
C8051F346@LQFP32 [CX3001] C8051F346-GQ@LQFP32 [CX3001]  
C8051F347@LQFP32 [CX3001] C8051F347-GQ@LQFP32 [CX3001]  
C8051F348@TQFP48 [CX3007] C8051F348-GQ@TQFP48 [CX3007]  
C8051F349@LQFP32 [CX3001] C8051F349-GQ@LQFP32 [CX3001]  
C8051F34A@LQFP32 [CX3001] C8051F34A-GQ@LQFP32 [CX3001]  
C8051F34B@LQFP32 [CX3001] C8051F34B-GQ@LQFP32 [CX3001]  
C8051F34C@TQFP48 [CX3007] C8051F34D@LQFP32 [CX3001]  
C8051F350-GQ@LQFP32 [CX3001] C8051F351-GM@QFN28 [CX4013]  
C8051F352-GQ@LQFP32 [CX3001] C8051F353-GM@QFN28 [CX4013]  
C8051F360@QFP48 [CX3007] C8051F361@QFP32 [CX3001]  
C8051F362@QFN28 [CX4013] C8051F363@QFP48 [CX3007]  
C8051F364@QFP32 [CX3001] C8051F365@QFN28 [CX4013]  
C8051F366@QFP32 [CX3001] C8051F367@QFN28 [CX4013]  
C8051F368@QFP32 [CX3001] C8051F369@QFN28 [CX4013]  
C8051F370-A-GM [CX4012] C8051F370-GM [CX4012]  
C8051F371-A-GM [CX4012] C8051F371-GM [CX4012]  
C8051F374-A-GM [CX4012] C8051F374-GM [CX4012]  
C8051F375-A-GM [CX4012] C8051F375-GM [CX4012]  
C8051F380@TQFP48 [CX3007] C8051F381@QFN32 [CX4015]  
C8051F381@TQFP32 [CX3001] C8051F382@TQFP48 [CX3007]  
C8051F383@QFN32 [CX4015] C8051F383@TQFP32 [CX3001]  
C8051F384@TQFP48 [CX3007] C8051F385@QFN32 [CX4015]  
C8051F385@TQFP32 [CX3001] C8051F386@TQFP48 [CX3007]  
C8051F387@QFN32 [CX4015] C8051F387@TQFP32 [CX3001]  
C8051F390-A-GM [CX4012] C8051F390-GM [CX4012]  
C8051F391-A-GM [CX4012] C8051F391-GM [CX4012]  
C8051F392-A-GM [CX4011] C8051F392-GM [CX4011]  
C8051F393-A-GM [CX4011] C8051F393-GM [CX4011]  
C8051F394-A-GM [CX4012] C8051F394-GM [CX4012]  
C8051F395-A-GM [CX4012] C8051F395-GM [CX4012]  
C8051F396-A-GM [CX4011] C8051F396-GM [CX4011]  
C8051F397-A-GM [CX4011] C8051F397-GM [CX4011]  
C8051F398-A-GM [CX4011] C8051F398-GM [CX4011]  
C8051F399-A-GM [CX4011] C8051F399-GM [CX4011]  
C8051F410@LQFP32 [CX3001] C8051F410-GQ@LQFP32 [CX3001]  
C8051F411@QFN28 [CX4013] C8051F411-GM@QFN28 [CX4013]  
C8051F412@LQFP32 [CX3001] C8051F412-GQ@LQFP32 [CX3001]  
C8051F413@QFN28 [CX4013] C8051F413-GM@QFN28 [CX4013]

C8051F500-IM@QFN48 [CX4021]	C8051F500-IQ@QFP48 [CX3007]
C8051F501-IM@QFN48 [CX4021]	C8051F501-IQ@QFP48 [CX3007]
C8051F502-IM@QFN32 [CX4015]	C8051F502-IQ@QFP32 [CX3001]
C8051F503-IM@QFN32 [CX4015]	C8051F503-IQ@QFP32 [CX3001]
C8051F504-IM@QFN48 [CX4021]	C8051F504-IQ@QFP48 [CX3007]
C8051F505-IM@QFN48 [CX4021]	C8051F505-IQ@QFP48 [CX3007]
C8051F506-IM@QFN32 [CX4015]	C8051F506-IQ@QFP32 [CX3001]
C8051F507-IM@QFN32 [CX4015]	C8051F507-IQ@QFP32 [CX3001]
C8051F508-IM@QFN40 [CX4017]	C8051F509-IM@QFN40 [CX4017]
C8051F510-IM@QFN40 [CX4017]	C8051F511-IM@QFN40 [CX4017]
C8051F520A-IM@QFN10 [CX4007]	C8051F520-IM@QFN10 [CX4007]
C8051F521A-IM@QFN10 [CX4007]	C8051F521-IM@QFN10 [CX4007]
C8051F523A-IM@QFN10 [CX4007]	C8051F523-IM@QFN10 [CX4007]
C8051F524A-IM@QFN10 [CX4007]	C8051F524-IM@QFN10 [CX4007]
C8051F526A-IM@QFN10 [CX4007]	C8051F526-IM@QFN10 [CX4007]
C8051F527A-IM@QFN10 [CX4007]	C8051F527-IM@QFN10 [CX4007]
C8051F530A-IM@QFN20 [CX4011]	C8051F530A-IT@TSSOP20 [CX1000]
C8051F530-IM@QFN20 [CX4011]	C8051F530-IT@TSSOP20 [CX1000]
C8051F531A-IM@QFN20 [CX4011]	C8051F531A-IT@TSSOP20 [CX1000]
C8051F531-IM@QFN20 [CX4011]	C8051F531-IT@TSSOP20 [CX1000]
C8051F533A-IM@QFN20 [CX4011]	C8051F533A-IT@TSSOP20 [CX1000]
C8051F533-IM@QFN20 [CX4011]	C8051F533-IT@TSSOP20 [CX1000]
C8051F534A-IM@QFN20 [CX4011]	C8051F534A-IT@TSSOP20 [CX1000]
C8051F534-IM@QFN20 [CX4011]	C8051F534-IT@TSSOP20 [CX1000]
C8051F536A-IM@QFN20 [CX4011]	C8051F536A-IT@TSSOP20 [CX1000]
C8051F536-IM@QFN20 [CX4011]	C8051F536-IT@TSSOP20 [CX1000]
C8051F537A-IM@QFN20 [CX4011]	C8051F537A-IT@TSSOP20 [CX1000]
C8051F537-IM@QFN20 [CX4011]	C8051F537-IT@TSSOP20 [CX1000]
C8051F540-IM@QFN32 [CX4015]	C8051F540-IQ@QFP32 [CX3001]
C8051F541-IM@QFN32 [CX4015]	C8051F541-IQ@QFP32 [CX3001]
C8051F542-IM@QFN24 [CX4012]	C8051F543-IM@QFN24 [CX4012]
C8051F544-IM@QFN32 [CX4015]	C8051F544-IQ@QFP32 [CX3001]
C8051F545-IM@QFN32 [CX4015]	C8051F545-IQ@QFP32 [CX3001]
C8051F546-IM@QFN24 [CX4012]	C8051F547-IM@QFN24 [CX4012]
C8051F550-IM@QFN24 [CX4012]	C8051F551-IM@QFN24 [CX4012]
C8051F552-IM@QFN24 [CX4012]	C8051F553-IM@QFN24 [CX4012]
C8051F554-IM@QFN24 [CX4012]	C8051F555-IM@QFN24 [CX4012]
C8051F556-IM@QFN24 [CX4012]	C8051F557-IM@QFN24 [CX4012]
C8051F560-IM@QFN32 [CX4015]	C8051F560-IQ@QFP32 [CX3001]
C8051F561-IM@QFN32 [CX4015]	C8051F561-IQ@QFP32 [CX3001]
C8051F562-IM@QFN32 [CX4015]	C8051F562-IQ@QFP32 [CX3001]
C8051F563-IM@QFN32 [CX4015]	C8051F563-IQ@QFP32 [CX3001]
C8051F564-IM@QFN32 [CX4015]	C8051F564-IQ@QFP32 [CX3001]
C8051F565-IM@QFN32 [CX4015]	C8051F565-IQ@QFP32 [CX3001]
C8051F566-IM@QFN32 [CX4015]	C8051F566-IQ@QFP32 [CX3001]
C8051F567-IM@QFN32 [CX4015]	C8051F567-IQ@QFP32 [CX3001]
C8051F568-IM@QFN40 [CX4017]	C8051F569-IM@QFN40 [CX4017]
C8051F570-IM@QFN40 [CX4017]	C8051F571-IM@QFN40 [CX4017]
C8051F572-IM@QFN40 [CX4017]	C8051F573-IM@QFN40 [CX4017]
C8051F574-IM@QFN40 [CX4017]	C8051F575-IM@QFN40 [CX4017]
C8051F580-AM@QFN48 [CX4021]	C8051F580-AQ@QFP48 [CX3047]
C8051F580-IM@QFN48 [CX4021]	C8051F580-IQ@QFP48 [CX3047]
C8051F581-AM@QFN48 [CX4021]	C8051F581-AQ@QFP48 [CX3047]
C8051F581-IM@QFN48 [CX4021]	C8051F581-IQ@QFP48 [CX3047]
C8051F582-AM@QFN32 [CX4015]	C8051F582-AQ@QFP32 [CX3001]
C8051F582-IM@QFN32 [CX4015]	C8051F582-IQ@QFP32 [CX3001]
C8051F583-AM@QFN32 [CX4015]	C8051F583-AQ@QFP32 [CX3001]
C8051F583-IM@QFN32 [CX4015]	C8051F583-IQ@QFP32 [CX3001]
C8051F584-AM@QFN48 [CX4021]	C8051F584-AQ@QFP48 [CX3047]

C8051F584-IM@QFN48 [CX4021]  
C8051F585-AM@QFN48 [CX4021]  
C8051F585-IM@QFN48 [CX4021]  
C8051F586-AM@QFN32 [CX4015]  
C8051F586-IM@QFN32 [CX4015]  
C8051F587-AM@QFN32 [CX4015]  
C8051F587-IM@QFN32 [CX4015]  
C8051F588-AM@QFN40 [CX4017]  
C8051F589-AM@QFN40 [CX4017]  
C8051F590-AM@QFN40 [CX4017]  
C8051F591-AM@QFN40 [CX4017]  
C8051F700-GQ@QFP64 [CX3011]  
C8051F702-GQ@QFP64 [CX3011]  
C8051F704-GM@QFN48 [CX4021]  
C8051F705-GM@QFN48 [CX4021]  
C8051F706-GM@QFN48 [CX4021]  
C8051F707-GM@QFN48 [CX4021]  
C8051F708-GQ@QFP64 [CX3011]  
C8051F710-GQ@QFP64 [CX3011]  
C8051F712-GM@QFN48 [CX4021]  
C8051F713-GM@QFN48 [CX4021]  
C8051F714-GM@QFN48 [CX4021]  
C8051F715-GM@QFN48 [CX4021]  
C8051F716-GM [CX4015]  
C8051F750B-GM [CX4021]  
C8051F750-GM [CX4021]  
C8051F751B-GM [CX4015]  
C8051F752B-GM [CX4012]  
C8051F755B-GM [CX4021]  
C8051F755-GM [CX4021]  
C8051F756B-GM [CX4015]  
C8051F757B-GM [CX4012]  
C8051F760-GM [CX4021]  
C8051F761-GM [CX4015]  
C8051F765-GM [CX4021]  
C8051F766-GM [CX4015]  
C8051F800-GM@QFN20 [CX4011]  
C8051F801-GM@QFN20 [CX4011]  
C8051F802-GM@QFN20 [CX4011]  
C8051F803-GS@SOIC16 [CX1016]  
C8051F805-GS@SOIC16 [CX1016]  
C8051F806-GU@QSOP24 [CX1001]  
C8051F807-GU@QSOP24 [CX1001]  
C8051F808-GU@QSOP24 [CX1001]  
C8051F810-GS@SOIC16 [CX1016]  
C8051F812-GM@QFN20 [CX4011]  
C8051F813-GM@QFN20 [CX4011]  
C8051F814-GM@QFN20 [CX4011]  
C8051F815-GS@SOIC16 [CX1016]  
C8051F817-GS@SOIC16 [CX1016]  
C8051F818-GU@QSOP24 [CX1001]  
C8051F819-GU@QSOP24 [CX1001]  
C8051F820-GU@QSOP24 [CX1001]  
C8051F822-GS@SOIC16 [CX1016]  
C8051F824-GS@SOIC16 [CX1016]  
C8051F826-GS@SOIC16 [CX1016]  
C8051F828-GS@SOIC16 [CX1016]  
C8051F830-GS@SOIC16 [CX1016]  
C8051F832-GS@SOIC16 [CX1016]

C8051F584-IQ@QFP48 [CX3047]  
C8051F585-AQ@QFP48 [CX3047]  
C8051F585-IQ@QFP48 [CX3047]  
C8051F586-AQ@QFP32 [CX3001]  
C8051F586-IQ@QFP32 [CX3001]  
C8051F587-AQ@QFP32 [CX3001]  
C8051F587-IQ@QFP32 [CX3001]  
C8051F588-IM@QFN40 [CX4017]  
C8051F589-IM@QFN40 [CX4017]  
C8051F590-IM@QFN40 [CX4017]  
C8051F591-IM@QFN40 [CX4017]  
C8051F701-GQ@QFP64 [CX3011]  
C8051F703-GQ@QFP64 [CX3011]  
C8051F704-GQ@QFP48 [CX3047]  
C8051F705-GQ@QFP48 [CX3047]  
C8051F706-GQ@QFP48 [CX3047]  
C8051F707-GQ@QFP48 [CX3047]  
C8051F709-GQ@QFP64 [CX3011]  
C8051F711-GQ@QFP64 [CX3011]  
C8051F712-GQ@QFP48 [CX3047]  
C8051F713-GQ@QFP48 [CX3047]  
C8051F714-GQ@QFP48 [CX3047]  
C8051F715-GQ@QFP48 [CX3047]  
C8051F717-GM [CX4012]  
C8051F750B-GM1 [CX4043]  
C8051F750-GM1 [CX4043]  
C8051F751-GM [CX4015]  
C8051F752-GM [CX4012]  
C8051F755B-GM1 [CX4043]  
C8051F755-GM1 [CX4043]  
C8051F756-GM [CX4015]  
C8051F757-GM [CX4012]  
C8051F760-GM1 [CX4043]  
C8051F762-GM [CX4012]  
C8051F765-GM1 [CX4043]  
C8051F767-GM [CX4012]  
C8051F800-GU@QSOP24 [CX1001]  
C8051F801-GU@QSOP24 [CX1001]  
C8051F802-GU@QSOP24 [CX1001]  
C8051F804-GS@SOIC16 [CX1016]  
C8051F806-GM@QFN20 [CX4011]  
C8051F807-GM@QFN20 [CX4011]  
C8051F808-GM@QFN20 [CX4011]  
C8051F809-GS@SOIC16 [CX1016]  
C8051F811-GS@SOIC16 [CX1016]  
C8051F812-GU@QSOP24 [CX1001]  
C8051F813-GU@QSOP24 [CX1001]  
C8051F814-GU@QSOP24 [CX1001]  
C8051F816-GS@SOIC16 [CX1016]  
C8051F818-GM@QFN20 [CX4011]  
C8051F819-GM@QFN20 [CX4011]  
C8051F820-GM@QFN20 [CX4011]  
C8051F821-GS@SOIC16 [CX1016]  
C8051F823-GS@SOIC16 [CX1016]  
C8051F825-GS@SOIC16 [CX1016]  
C8051F827-GS@SOIC16 [CX1016]  
C8051F829-GS@SOIC16 [CX1016]  
C8051F831-GS@SOIC16 [CX1016]  
C8051F833-GS@SOIC16 [CX1016]

C8051F834-GS@SOIC16 [CX1016]  
C8051F901-GM@QFN24 [CX4012]  
C8051F902-GM@QFN24 [CX4012]  
C8051F911-GM@QFN24 [CX4012]  
C8051F912-GM@QFN24 [CX4012]  
C8051F920-F-GM@QFN32 [CX4015]  
C8051F920-GM@QFN32 [CX4015]  
C8051F921-F-GM@QFN24 [CX4012]  
C8051F930-F-GM@QFN32 [CX4015]  
C8051F930-GM@QFN32 [CX4015]  
C8051F931-F-GM@QFN24 [CX4012]  
C8051F960A-GM [CX0001]  
C8051F960-GM [CX0001]  
C8051F961A-GM [CX4017]  
C8051F962A-GM [CX0001]  
C8051F962-GM [CX0001]  
C8051F963A-GM [CX4017]  
C8051F964A-GM [CX0001]  
C8051F964-GM [CX0001]  
C8051F965A-GM [CX4017]  
C8051F966A-GM [CX0001]  
C8051F966-GM [CX0001]  
C8051F967A-GM [CX4017]  
C8051F968A-GM [CX0001]  
C8051F968-GM [CX0001]  
C8051F969A-GM [CX4017]  
C8051F980-GM [CX4038]  
C8051F982-GM [CX4038]  
C8051F985-GM [CX4038]  
C8051F986-GU [CX1001]  
C8051F987-GU [CX1001]  
C8051F988-GU [CX1001]  
C8051F989-GU [CX1001]  
C8051F991-GM [CX4038]  
C8051F996-GU [CX1001]  
C8051F997-GU [CX1001]  
C8051T321-GM@QFN28 [CX4013]  
C8051T323-GM@QFN28 [CX4013]  
C8051T327-GM@QFN28 [CX4013]  
C8051T600@TSSOP14 [CX1016]  
C8051T601@TSSOP14 [CX1016]  
C8051T602@TSSOP14 [CX1016]  
C8051T603@TSSOP14 [CX1016]  
C8051T604@TSSOP14 [CX1016]  
C8051T605@TSSOP14 [CX1016]  
C8051T606@QFN10 [CX4035]  
C8051T610-GQ@LQFP32 [CX3001]  
C8051T610-GQ@LQFP32(old) [CX3001]  
C8051T611-GM@QFN28 [CX4013]  
C8051T612-GQ@LQFP32 [CX3001]  
C8051T612-GQ@LQFP32(old) [CX3001]  
C8051T613-GM@QFN28 [CX4013]  
C8051T614-GQ@LQFP32 [CX3001]  
C8051T614-GQ@LQFP32(old) [CX3001]  
C8051T615-GM@QFN28 [CX4013]  
C8051T616-GM@QFN24 [CX4012]  
C8051T617-GM@QFN24 [CX4012]  
C8051T620-GM@QFN32 [CX4015]  
C8051T622-GM@QFN24 [CX4012]

C8051F835-GS@SOIC16 [CX1016]  
C8051F901-GU@QSOP24 [CX1001]  
C8051F902-GU@QSOP24 [CX1001]  
C8051F911-GU@QSOP24 [CX1001]  
C8051F912-GU@QSOP24 [CX1001]  
C8051F920-F-GQ@LQFP32 [CX3001]  
C8051F920-GQ@LQFP32 [CX3001]  
C8051F921-GM@QFN24 [CX4012]  
C8051F930-F-GQ@LQFP32 [CX3001]  
C8051F930-GQ@LQFP32 [CX3001]  
C8051F931-GM@QFN24 [CX4012]  
C8051F960A-GQ [CX3016]  
C8051F960-GQ [CX3016]  
C8051F961-GM [CX4017]  
C8051F962A-GQ [CX3016]  
C8051F962-GQ [CX3016]  
C8051F963-GM [CX4017]  
C8051F964A-GQ [CX3016]  
C8051F964-GQ [CX3016]  
C8051F965-GM [CX4017]  
C8051F966A-GQ [CX3016]  
C8051F966-GQ [CX3016]  
C8051F967-GM [CX4017]  
C8051F968A-GQ [CX3016]  
C8051F968-GQ [CX3016]  
C8051F969-GM [CX4017]  
C8051F981-GM [CX4038]  
C8051F983-GM [CX4038]  
C8051F986-GM [CX4012]  
C8051F987-GM [CX4012]  
C8051F988-GM [CX4012]  
C8051F989-GM [CX4012]  
C8051F990-GM [CX4038]  
C8051F996-GM [CX4012]  
C8051F997-GM [CX4012]  
C8051T320-GQ@LQFP32 [CX3001]  
C8051T322-GQ@LQFP32 [CX3001]  
C8051T326-GM@QFN28 [CX4013]  
C8051T600@QFN11 [CX4007]  
C8051T601@QFN11 [CX4007]  
C8051T602@QFN11 [CX4007]  
C8051T603@QFN11 [CX4007]  
C8051T604@QFN11 [CX4007]  
C8051T605@QFN11 [CX4007]  
C8051T606@MSOP10 [CX1016]  
C8051T606@QFN11 [CX4007]  
  
C8051T611-GM@QFN28(old) [CX4013]  
  
C8051T613-GM@QFN28(old) [CX4013]  
  
C8051T615-GM@QFN28(old) [CX4013]  
C8051T616-GM@QFN24(old) [CX4012]  
C8051T617-GM@QFN24(old) [CX4012]  
C8051T621-GM@QFN32 [CX4015]  
C8051T623-GM@QFN24 [CX4012]

C8051T626-B-GM [CX4015]  
SI1020\_A\_GM(ISP) [CX0001]  
SI1022\_A\_GM(ISP) [CX0001]  
SI1024\_A\_GM(ISP) [CX0001]  
SI1026\_A\_GM(ISP) [CX0001]  
SI1030\_A\_GM(ISP) [CX0001]  
SI1032\_A\_GM(ISP) [CX0001]  
SI1034\_A\_GM(ISP) [CX0001]  
SI1036\_A\_GM(ISP) [CX0001]  
SI8250@LQFP32 [CX3001]  
SI8250-IM@QFN28 [CX4013]  
SI8251@LQFP32 [CX3001]  
SI8251-IM@QFN28 [CX4013]  
SI8252@LQFP32 [CX3001]  
SI8252-IM@QFN28 [CX4013]

C8051T627-B-GM [CX4015]  
SI1021\_A\_GM(ISP) [CX0001]  
SI1023\_A\_GM(ISP) [CX0001]  
SI1025\_A\_GM(ISP) [CX0001]  
SI1027\_A\_GM(ISP) [CX0001]  
SI1031\_A\_GM(ISP) [CX0001]  
SI1033\_A\_GM(ISP) [CX0001]  
SI1035\_A\_GM(ISP) [CX0001]  
SI1037\_A\_GM(ISP) [CX0001]  
SI8250@QFN28 [CX4013]  
SI8250-IQ@LQFP32 [CX3001]  
SI8251@QFN28 [CX4013]  
SI8251-IQ@LQFP32 [CX3001]  
SI8252@QFN28 [CX4013]  
SI8252-IQ@LQFP32 [CX3001]

## CYPRESS

### E(E) PROM/FRAM/NVRAM

CY14B256Q [CX0001]  
CY14B256Q@SOIC8 [CX1045]  
CY14C256Q@SOIC16 [CX1016]  
CY14E256Q [CX0001]  
CY14E256Q@SOIC8 [CX1045]  
CY27C010@PLCC32 [CX2032]  
CY27C020 [CX0001]  
CY27C020@TSOP32 [CX1002]  
CY27C040@PLCC32 [CX2032]  
CY27C256 [CX0001]  
CY27C256@TSOP28 [CX1024]  
CY27C512@PLCC32 [CX2032]  
CY27H010 [CX0001]  
CY27H010@TSOP32 [CX1002]  
CY27H256@PLCC32 [CX2032]  
CY27H512 [CX0001]  
CY27H512@TSOP28 [CX1024]  
CY7C225@PLCC28 [CX2028]  
CY7C225A@PLCC28 [CX2028]  
CY7C235@PLCC28 [CX3028]  
CY7C235A@PLCC28 [CX3028]  
CY7C243@PLCC28 [CX3028]  
CY7C244@PLCC28 [CX3028]  
CY7C245@PLCC28 [CX3028]  
CY7C245A@PLCC28 [CX3028]  
CY7C249@PLCC44 [CX2044]  
CY7C251@PLCC32 [CX3032]  
CY7C254@PLCC32 [CX3032]  
CY7C256@PLCC32 [CX2032]  
CY7C256A@PLCC32 [CX2032]  
CY7C258@PLCC28 [CX2028]  
CY7C261 [CX0001]  
CY7C263 [CX0001]  
CY7C264 [CX0001]  
CY7C265 [CX0001]  
CY7C266 [CX0001]  
CY7C268 [CX0001]  
CY7C269 [CX0001]

CY14B256Q@SOIC16 [CX1016]  
CY14C256Q [CX0001]  
CY14C256Q@SOIC8 [CX1045]  
CY14E256Q@SOIC16 [CX1016]  
CY27C010 [CX0001]  
CY27C010@TSOP32 [CX1002]  
CY27C020@PLCC32 [CX2032]  
CY27C040 [CX0001]  
CY27C040@TSOP32 [CX1002]  
CY27C256@PLCC32 [CX2032]  
CY27C512 [CX0001]  
CY27C512@TSOP28 [CX1024]  
CY27H010@PLCC32 [CX2032]  
CY27H256 [CX0001]  
CY27H256@TSOP28 [CX1024]  
CY27H512@PLCC32 [CX2032]  
CY7C225 [CX0001]  
CY7C225A [CX0001]  
CY7C235 [CX0001]  
CY7C235A [CX0001]  
CY7C243 [CX0001]  
CY7C244 [CX0001]  
CY7C245 [CX0001]  
CY7C245A [CX0001]  
CY7C248@PLCC44 [CX2044]  
CY7C251 [CX0001]  
CY7C254 [CX0001]  
CY7C256 [CX0001]  
CY7C256A [CX0001]  
CY7C258 [CX0001]  
CY7C259@PLCC44 [CX2044]  
CY7C261@PLCC28 [CX2028]  
CY7C263@PLCC28 [CX2028]  
CY7C264@PLCC28 [CX2028]  
CY7C265@PLCC28 [CX2028]  
CY7C266@PLCC32 [CX2032]  
CY7C268@PLCC32 [CX2032]  
CY7C269@PLCC28 [CX2028]



CY7C271 [CX0001]  
CY7C271A [CX0001]  
CY7C274 [CX0001]  
CY7C276(25HC)@PLCC44 [CX2044]  
CY7C276(30JC)@PLCC44 [CX2044]  
CY7C281@PLCC28 [CX3028]  
CY7C281A@PLCC28 [CX3028]  
CY7C282@PLCC28 [CX3028]  
CY7C282A@PLCC28 [CX3028]  
CY7C285@PLCC32 [CX3032]  
CY7C286@PLCC32 [CX3032]  
CY7C287@PLCC32 [CX3032]  
CY7C289@PLCC32 [CX3032]  
CY7C291@PLCC28 [CX3028]  
CY7C291A@PLCC28 [CX2028]  
CY7C292@PLCC28 [CX3028]  
CY7C292A@PLCC28 [CX2028]  
CY7C293A@PLCC28 [CX2028]

CY7C271@PLCC32 [CX2032]  
CY7C271A@PLCC32 [CX2032]  
CY7C274@PLCC32 [CX2032]  
CY7C276(25JC)@PLCC44 [CX2044]  
CY7C281 [CX0001]  
CY7C281A [CX0001]  
CY7C282 [CX0001]  
CY7C282A [CX0001]  
CY7C285 [CX0001]  
CY7C286 [CX0001]  
CY7C287 [CX0001]  
CY7C289 [CX0001]  
CY7C291 [CX0001]  
CY7C291A [CX0001]  
CY7C292 [CX0001]  
CY7C292A [CX0001]  
CY7C293A [CX0001]

#### DRAM & SRAM

CY62128@SOIC32 [CX1020]  
CY62128@VSOP32 [CX1003]  
CY62128L@SOJ32 [CX1039]  
CY62128LL@SOIC32 [CX1020]  
CY62128LL@VSOP32 [CX1003]  
CY7C1061@VFPGA48 [UN]  
CY7C192@SOJ28 [CX1038]

CY62128@SOJ32 [CX1039]  
CY62128L@SOIC32 [CX1020]  
CY62128L@VSOP32 [CX1003]  
CY62128LL@SOJ32  
CY7C1061@TSOP54 [CX1010]  
CY7C192 [CX0001]

#### PLD

CY22381@SOIC8 [CX1045]  
CY22393@TSSOP16 [CX1000]  
CY22395@TSSOP16 [CX1000]  
CY2292@SOIC16 [CX1016]  
CY37032@PLCC44 [CX2044]  
CY37032V@PLCC44 [CX2044]  
CY37064@PLCC44 [CX2044]  
CY37064@TQFP100 [CX3021]  
CY37064V@PLCC84 [CX2084]  
CY7C342B@PLCC68 [CX2068]  
CY7C346B@PQFP100 [CX3022]  
CY7C371@TQFP44 [CX3003]  
CY7C371I@TQFP44 [CX3003]  
CY7C372@TQFP44 [CX3003]  
CY7C372I@TQFP44 [CX3003]  
CY7C373@TQFP100 [CX3021]  
CY7C373I@TQFP100 [CX3021]  
CY7C374@TQFP100 [CX3021]  
CY7C374I@TQFP100 [CX3021]  
PALC16L8@PLCC20 [CX2020]  
PALC16L8L@PLCC20 [CX2020]  
PALC16R4@PLCC20 [CX2020]  
PALC16R4L@PLCC20 [CX2020]  
PALC16R6@PLCC20 [CX2020]  
PALC16R6L@PLCC20 [CX2020]  
PALC16R8@PLCC20 [CX2020]  
PALC16R8L@PLCC20 [CX2020]

CY22392@TSSOP16 [CX1000]  
CY22394@TSSOP16 [CX1000]  
CY2291@SOIC20 [CX1033]  
CY2295@SSOP28 [CX1026]  
CY37032@TQFP44 [CX3003]  
CY37032V@TQFP44 [CX3003]  
CY37064@PLCC84 [CX2084]  
CY37064V@PLCC44 [CX2044]  
CY37064V@TQFP100 [CX3021]  
CY7C346B@PLCC84 [CX2084]  
CY7C371@PLCC44 [CX2044]  
CY7C371I@PLCC44 [CX2044]  
CY7C372@PLCC44 [CX2044]  
CY7C372I@PLCC44 [CX2044]  
CY7C373@PLCC84 [CX2084]  
CY7C373I@PLCC84 [CX2084]  
CY7C374@PLCC84 [CX2084]  
CY7C374I@PLCC84 [CX2084]  
PALC16L8 [CX0001]  
PALC16L8L [CX0001]  
PALC16R4 [CX0001]  
PALC16R4L [CX0001]  
PALC16R6 [CX0001]  
PALC16R6L [CX0001]  
PALC16R8 [CX0001]  
PALC16R8L [CX0001]  
PALC22V10D [CX0001]

PALC22V10D@PLCC28 [CX2028]  
PALCE16V8@PLCC20 [CX2020]  
PALCE20V8@PLCC28 [CX2028]  
PALCE20V8L@PLCC28 [CX2028]  
PALCE22V10@PLCC28 [CX2028]  
PLDC20G10@PLCC28 [CX2028]  
PLDC20G10B@PLCC28 [CX2028]  
PLDC20RA10@PLCC28 [CX0001]

PALCE16V8 [CX0001]  
PALCE20V8 [CX0001]  
PALCE20V8L [CX0001]  
PALCE22V10 [CX0001]  
PLDC20G10 [CX0001]  
PLDC20G10B [CX0001]  
PLDC20RA10 [CX0001]

#### MICROCONTROLLER

CG6457AM@SSOP20 [CX1026]  
CG6457AMB@SSOP20 [CX1026]  
CG6462AM@SOIC8 (ISP) [CX0001]  
CY14B256@SOIC32 [CX1069]  
CY14B256L@SOIC32 [CX1069]  
CY7C53120E2@SOIC32 [CX1020]  
CY7C53120E2A@SOIC32 [CX1020]  
CY7C53120E4@SOIC32 [CX1020]  
CY7C53120E4A@SOIC32 [CX1020]  
CY7C60113@SSOP28 [CX1026]  
CY7C60113C@SSOP28 [CX1026]  
CY7C60123 [CX0001]  
CY7C60123@SSOP48 [CX1028]  
CY7C60123C [CX0001]  
CY7C60123C@SSOP48 [CX1028]  
CY7C60223 [CX0001]  
CY7C60223@QSOP24 [CX1001]  
CY7C60223@SOIC24 [CX1033]  
CY7C60223C [CX0001]  
CY7C60223C@QSOP24 [CX1001]  
CY7C60223C@SOIC24 [CX1033]  
CY7C60323@MLF32 [CX4015]  
CY7C60323@SSOP28 [CX1026]  
CY7C60323B@MLF32 [CX4015]  
CY7C60333@MLF32 [CX4015]  
CY7C60333B@MLF32 [CX4015]  
CY7C60443@QFN32 (ISP) [CX0001]  
CY7C60445@QFN32 (ISP) [CX0001]  
CY7C60455@QFN48 (ISP) [CX0001]  
CY7C60456@QFN48 (ISP) [CX0001]  
CY7C63000@SOIC20 [CX1033]  
CY7C63000A@SOIC20 [CX1033]  
CY7C63000C@SOIC20 [CX1033]  
CY7C63001@SOIC20 [CX1033]  
CY7C63001A@SOIC20 [CX1033]  
CY7C63001C@SOIC20 [CX1033]  
CY7C63100@SOIC24 [CX1033]  
CY7C63100A@SOIC24 [CX1033]  
CY7C63100C@SOIC24 [CX1033]  
CY7C63101@SOIC24 [CX1033]  
CY7C63101A@SOIC24 [CX1033]  
CY7C63101C@SOIC24 [CX1033]  
CY7C63200@SOIC18 [CX1033]  
CY7C63200A@SOIC18 [CX1033]  
CY7C63200C@SOIC18 [CX1033]  
CY7C63201@SOIC18 [CX1033]  
CY7C63201A@SOIC18 [CX1033]  
CY7C63201C@SOIC18 [CX1033]

CG6457AM@SSOP20 (ISP) [CX0001]  
CG6462AM@SOIC8 [CX1045]  
CG6462AMB@SOIC8 [CX1045]  
CY14B256@SSOP48 [CX1028]  
CY14B256L@SSOP48 [CX1028]  
CY7C53120E2@TQFP44 [CX3002]  
CY7C53120E2A@TQFP44 [CX3002]  
CY7C53120E4@TQFP44 [CX3002]  
CY7C53120E4A@TQFP44 [CX3002]  
CY7C60113@SSOP28 (ISP) [CX0001]  
CY7C60113C@SSOP28 (ISP) [CX0001]  
CY7C60123 (ISP) [CX0001]  
CY7C60123@SSOP48 (ISP) [CX0001]  
CY7C60123C (ISP) [CX0001]  
CY7C60123C@SSOP48 (ISP) [CX0001]  
CY7C60223 (ISP) [CX0001]  
CY7C60223@QSOP24 (ISP) [CX0001]  
CY7C60223@SOIC24 (ISP) [CX0001]  
CY7C60223C (ISP) [CX0001]  
CY7C60223C@QSOP24 (ISP) [CX0001]  
CY7C60223C@SOIC24 (ISP) [CX0001]  
CY7C60323@MLF32 (ISP) [CX0001]  
CY7C60323@SSOP28 (ISP) [CX0001]  
CY7C60323B@SSOP28 [CX1026]  
CY7C60333@MLF32 (ISP) [CX0001]  
CY7C60443@QFN32 [CX4015]  
CY7C60445@QFN32 [CX4015]  
CY7C60455@QFN48 [CX4021]  
CY7C60456@QFN48 [CX4021]  
CY7C63000 [CX0001]  
CY7C63000A [CX0001]  
CY7C63000C [CX0001]  
CY7C63001 [CX0001]  
CY7C63001A [CX0001]  
CY7C63001C [CX0001]  
CY7C63100 [CX0001]  
CY7C63100A [CX0001]  
CY7C63100C [CX0001]  
CY7C63101 [CX0001]  
CY7C63101A [CX0001]  
CY7C63101C [CX0001]  
CY7C63200 [CX0001]  
CY7C63200A [CX0001]  
CY7C63200C [CX0001]  
CY7C63201 [CX0001]  
CY7C63201A [CX0001]  
CY7C63201C [CX0001]  
CY7C63221 [CX0001]

CY7C63221A [CX0001]  
CY7C63231@SOIC18 [CX1033]  
CY7C63231A@SOIC18 [CX1033]  
CY7C63310(ISP) [CX0001]  
CY7C63310@SOIC16(ISP) [CX0001]  
CY7C63310C(ISP) [CX0001]  
CY7C63310C@SOIC16(ISP) [CX0001]  
CY7C63411(dip48) [CX0001]  
CY7C63411C(dip40) [CX0001]  
CY7C63411C@SSOP48 [CX1028]  
CY7C63412(dip48) [CX0001]  
CY7C63412C(dip40) [CX0001]  
CY7C63412C@SSOP48 [CX1028]  
CY7C63413(dip48) [CX0001]  
CY7C63413C(dip40) [CX0001]  
CY7C63413C@SSOP48 [CX1028]  
CY7C63511@SSOP48 [CX1028]  
CY7C63511C@SSOP48 [CX1028]  
CY7C63512@SSOP48 [CX1028]  
CY7C63512C@SSOP48 [CX1028]  
CY7C63513@SSOP48 [CX1028]  
CY7C63513C@SSOP48 [CX1028]  
CY7C63722@SOIC18 [CX1033]  
CY7C63722C@SOIC18 [CX1033]  
CY7C63723@SOIC18 [CX1033]  
CY7C63723C@SOIC18 [CX1033]  
CY7C63742@QSOP24 [CX1025]  
CY7C63742C [CX0001]  
CY7C63742C@SOIC24 [CX1033]  
CY7C63743@QSOP24 [CX1025]  
CY7C63743C [CX0001]  
CY7C63743C@SOIC24 [CX1033]  
CY7C63801(ISP) [CX0001]  
CY7C63801@SOIC16(ISP) [CX0001]  
CY7C63801C(ISP) [CX0001]  
CY7C63801C@SOIC16(ISP) [CX0001]  
CY7C63803@SOIC16(ISP) [CX0001]  
CY7C63803C@SOIC16(ISP) [CX0001]  
CY7C63813(ISP) [CX0001]  
CY7C63813@SOIC18(ISP) [CX0001]  
CY7C63813C(ISP) [CX0001]  
CY7C63813C@SOIC18(ISP) [CX0001]  
CY7C63823(ISP) [CX0001]  
CY7C63823@QSOP24(ISP) [CX0001]  
CY7C63823@SOIC24(ISP) [CX0001]  
CY7C63823C(ISP) [CX0001]  
CY7C63823C@QSOP24(ISP) [CX0001]  
CY7C63823C@SOIC24(ISP) [CX0001]  
CY7C63833@QFN32(ISP) [CX0001]  
CY7C63833C@QFN32(ISP) [CX0001]  
CY7C63903@SSOP28(ISP) [CX0001]  
CY7C63903C@SSOP28(ISP) [CX0001]  
CY7C63913(ISP) [CX0001]  
CY7C63913C(ISP) [CX0001]  
CY7C63923@SSOP48(ISP) [CX0001]  
CY7C63923C@SSOP48(ISP) [CX0001]  
CY7C64011@SOIC28 [CX1033]  
CY7C64011C@SOIC28 [CX1033]  
CY7C64012@SOIC28 [CX1033]

CY7C63231 [CX0001]  
CY7C63231A [CX0001]  
CY7C63310 [CX0001]  
CY7C63310@SOIC16 [CX1016]  
CY7C63310C [CX0001]  
CY7C63310C@SOIC16 [CX1016]  
CY7C63411(dip40) [CX0001]  
CY7C63411@SSOP48 [CX1028]  
CY7C63411C(dip48) [CX0001]  
CY7C63412(dip40) [CX0001]  
CY7C63412@SSOP48 [CX1028]  
CY7C63412C(dip48) [CX0001]  
CY7C63413(dip40) [CX0001]  
CY7C63413@SSOP48 [CX1028]  
CY7C63413C(dip48) [CX0001]  
CY7C63511(dip48) [CX0001]  
CY7C63511C(dip48) [CX0001]  
CY7C63512(dip48) [CX0001]  
CY7C63512C(dip48) [CX0001]  
CY7C63513(dip48) [CX0001]  
CY7C63513C(dip48) [CX0001]  
CY7C63722 [CX0001]  
CY7C63722C [CX0001]  
CY7C63723 [CX0001]  
CY7C63723C [CX0001]  
CY7C63742 [CX0001]  
CY7C63742@SOIC24 [CX1033]  
CY7C63742C@QSOP24 [CX1025]  
CY7C63743 [CX0001]  
CY7C63743@SOIC24 [CX1033]  
CY7C63743C@QSOP24 [CX1025]  
CY7C63801 [CX0001]  
CY7C63801@SOIC16 [CX1016]  
CY7C63801C [CX0001]  
CY7C63801C@SOIC16 [CX1016]  
CY7C63803@SOIC16 [CX1016]  
CY7C63803C@SOIC16 [CX1016]  
CY7C63813 [CX0001]  
CY7C63813@SOIC18 [CX1033]  
CY7C63813C [CX0001]  
CY7C63813C@SOIC18 [CX1033]  
CY7C63823 [CX0001]  
CY7C63823@QSOP24 [CX1001]  
CY7C63823@SOIC24 [CX1033]  
CY7C63823C [CX0001]  
CY7C63823C@QSOP24 [CX1001]  
CY7C63823C@SOIC24 [CX1033]  
CY7C63833@QFN32 [CX4015]  
CY7C63833C@QFN32 [CX4015]  
CY7C63903@SSOP28 [CX1026]  
CY7C63903C@SSOP28 [CX1026]  
CY7C63913 [CX0001]  
CY7C63913C [CX0001]  
CY7C63923@SSOP48 [CX1028]  
CY7C63923C@SSOP48 [CX1028]  
CY7C64011 [CX0001]  
CY7C64011C [CX0001]  
CY7C64012 [CX0001]  
CY7C64012C [CX0001]

CY7C64012C@SOIC28 [CX1033]  
CY7C64013@SOIC28 [CX1033]  
CY7C64013C@SOIC28 [CX1033]  
CY7C64111@SSOP48 [CX1028]  
CY7C64111C@SSOP48 [CX1028]  
CY7C64112@SSOP48 [CX1028]  
CY7C64112C@SSOP48 [CX1028]  
CY7C64113@SSOP48 [CX1028]  
CY7C64113C@SSOP48 [CX1028]  
CY7C64215@MLF56(ISP) [CX0001]  
CY7C64215@SSOP28(ISP) [CX0001]  
CY7C64315@QFN16(ISP) [CX0001]  
CY7C64316@QFN16(ISP) [CX0001]  
CY7C64343@QFN32(ISP) [CX0001]  
CY7C64345@QFN32(ISP) [CX0001]  
CY7C64355@QFN48(ISP) [CX0001]  
CY7C64356@QFN48(ISP) [CX0001]  
CY7C65013@SSOP48 [CX1028]  
CY7C65013C@SSOP48 [CX1028]  
CY7C65113@SOIC28 [CX1033]  
CY7C65113C@SOIC28 [CX1033]  
CY7C66011@SSOP48 [CX1028]  
CY7C66011C@SSOP48 [CX1028]  
CY7C66012@SSOP48 [CX1028]  
CY7C66012C@SSOP48 [CX1028]  
CY7C66013@SSOP48 [CX1028]  
CY7C66013C@SSOP48 [CX1028]  
CY7C66111@SSOP56 [CX1054]  
CY7C66111C@QFN56 [CX4022]  
CY7C66111C@TSOP56 [CX1055]  
CY7C66112@SSOP56 [CX1054]  
CY7C66112C@QFN56 [CX4022]  
CY7C66112C@TSOP56 [CX1055]  
CY7C66113@SSOP56 [CX1054]  
CY7C66113C@QFN56 [CX4022]  
CY7C66113C@TSOP56 [CX1055]  
CY8C20000@MLF48(ISP) [CX0001]  
CY8C20045-24SXI [CX1030]  
CY8C20055-24SXI [CX1030]  
CY8C20065-24SXI [CX1030]  
CY8C20134@SOIC8 [CX1045]  
CY8C20224@MLF16(ISP) [CX0001]  
CY8C20234@MLF16(ISP) [CX0001]  
CY8C20236A@MLF16 [CX4008]  
CY8C20237@SOIC16 [CX1030]  
CY8C20237S@SOIC16 [CX1030]  
CY8C20246@QFN16(ISP) [CX0001]  
CY8C20247@MLF16 [CX4008]  
CY8C20247S@MLF16 [CX4008]  
CY8C20266@QFN16 [CX4008]  
CY8C20324@MLF24 [CX4012]  
CY8C20334@MLF24 [CX4012]  
CY8C20336A@MLF24 [CX4012]  
CY8C20337S@MLF24 [CX4012]  
CY8C20346@QFN24(ISP) [CX0001]  
CY8C20347@MLF24 [CX4012]  
CY8C20366@QFN24 [CX4012]  
CY8C20396A@MLF24 [CX4012]  
CY8C20397S@MLF24 [CX4012]  
CY7C64013 [CX0001]  
CY7C64013C [CX0001]  
CY7C64111 [CX0001]  
CY7C64111C [CX0001]  
CY7C64112 [CX0001]  
CY7C64112C [CX0001]  
CY7C64113 [CX0001]  
CY7C64113C [CX0001]  
CY7C64215@MLF56 [CX4022]  
CY7C64215@SSOP28 [CX1026]  
CY7C64315@QFN16 [CX4008]  
CY7C64316@QFN16 [CX4008]  
CY7C64343@QFN32 [CX4015]  
CY7C64345@QFN32 [CX4015]  
CY7C64355@QFN48 [CX4021]  
CY7C64356@QFN48 [CX4021]  
CY7C65013 [CX0001]  
CY7C65013C [CX0001]  
CY7C65113 [CX0001]  
CY7C65113C [CX0001]  
CY7C66011 [CX0001]  
CY7C66011C [CX0001]  
CY7C66012 [CX0001]  
CY7C66012C [CX0001]  
CY7C66013 [CX0001]  
CY7C66013C [CX0001]  
CY7C66111@QFN56 [CX4022]  
CY7C66111@TSOP56 [CX1055]  
CY7C66111C@SSOP56 [CX1054]  
CY7C66112@QFN56 [CX4022]  
CY7C66112@TSOP56 [CX1055]  
CY7C66112C@SSOP56 [CX1054]  
CY7C66113@QFN56 [CX4022]  
CY7C66113@TSOP56 [CX1055]  
CY7C66113C@SSOP56 [CX1054]  
CY8C20000@MLF48 [CX4021]  
CY8C20045-24LKXI [CX4008]  
CY8C20055-24LKXI [CX4008]  
CY8C20065-24LKXI [CX4008]  
CY8C20066A@MLF48 [CX4021]  
CY8C20224@MLF16 [CX4008]  
CY8C20234@MLF16 [CX4008]  
CY8C20234@SOIC16 [CX1016]  
CY8C20237@MLF16 [CX4008]  
CY8C20237S@MLF16 [CX4008]  
CY8C20246@QFN16 [CX4008]  
CY8C20246A@MLF16 [CX4008]  
CY8C20247@SOIC16 [CX1030]  
CY8C20247S@SOIC16 [CX1030]  
CY8C20266@QFN16(ISP) [CX0001]  
CY8C20324@MLF24(ISP) [CX0001]  
CY8C20334@MLF24(ISP) [CX0001]  
CY8C20337@MLF24 [CX4012]  
CY8C20346@QFN24 [CX4012]  
CY8C20346A@MLF24 [CX4012]  
CY8C20347S@MLF24 [CX4012]  
CY8C20366@QFN24(ISP) [CX0001]  
CY8C20397@MLF24 [CX4012]  
CY8C20424@MLF32 [CX4015]

CY8C20424@MLF32(ISP) [CX0001]  
CY8C20434@MLF32(ISP) [CX0001]  
CY8C20437@MLF32 [CX4015]  
CY8C20446@QFN32 [CX4015]  
CY8C20446A@MLF32 [CX4015]  
CY8C20447S@MLF32 [CX4015]  
CY8C20466@QFN32(ISP) [CX0001]  
CY8C20467@MLF32 [CX4015]  
CY8C20496A@MLF32 [CX4015]  
CY8C20497S@MLF32 [CX4015]  
CY8C20534@BGA30 [CX0001]  
CY8C20534@SSOP28(ISP) [CX0001]  
CY8C20537@SSOP48 [CX1028]  
CY8C20546@SSOP48 [CX1028]  
CY8C20546A@SSOP48 [CX1028]  
CY8C20547S@SSOP48 [CX1028]  
CY8C20566@SSOP48(ISP) [CX0001]  
CY8C20567@SSOP48 [CX1028]  
CY8C20636A@MLF48 [CX4021]  
CY8C20637S@MLF48 [CX4021]  
CY8C20646@QFN48(ISP) [CX0001]  
CY8C20647@MLF48 [CX4021]  
CY8C20666@QFN48 [CX4021]  
CY8C20666A@MLF48 [CX4021]  
CY8C20667S@MLF48 [CX4021]  
CY8C20767-24FDXC [BBBB]  
CY8C21123@SOIC8(ISP) [CX0001]  
CY8C21223@SOIC16 [CX1016]  
CY8C21223B@SOIC16 [CX1016]  
CY8C21234@SOIC16(ISP) [CX0001]  
CY8C21323@MLF24 [CX4012]  
CY8C21323@SSOP20 [CX1026]  
CY8C21323B@MLF24 [CX4012]  
CY8C21334@SSOP20 [CX1026]  
CY8C21334B@SSOP20 [CX1026]  
CY8C21345@SSOP28 [CX1026]  
CY8C21434@MLF32(ISP) [CX0001]  
CY8C21534@SSOP28 [CX1026]  
CY8C21534B@SSOP28 [CX1026]  
CY8C21634@MLF32(ISP) [CX0001]  
CY8C22345@SOIC28 [CX1033]  
CY8C22545@TQFP44 [CX3005]  
CY8C24123(ISP) [CX0001]  
CY8C24123@SOIC8(ISP) [CX0001]  
CY8C24123A(ISP) [CX0001]  
CY8C24123A@SOIC8(ISP) [CX0001]  
CY8C24223(ISP) [CX0001]  
CY8C24223@SOIC20(ISP) [CX0001]  
CY8C24223@SSOP20(ISP) [CX0001]  
CY8C24223A(ISP) [CX0001]  
CY8C24223A@SOIC20(ISP) [CX0001]  
CY8C24223A@SSOP20(ISP) [CX0001]  
CY8C24423(ISP) [CX0001]  
CY8C24423@MLF32(ISP) [CX0001]  
CY8C24423@SOIC28(ISP) [CX0001]  
CY8C24423@SSOP28(ISP) [CX0001]  
CY8C24423A(ISP) [CX0001]  
CY8C24423A@MLF32(ISP) [CX0001]  
CY8C24423A@SOIC28(ISP) [CX0001]  
CY8C20434@MLF32 [CX4015]  
CY8C20436A@MLF32 [CX4015]  
CY8C20437S@MLF32 [CX4015]  
CY8C20446@QFN32(ISP) [CX0001]  
CY8C20447@MLF32 [CX4015]  
CY8C20466@QFN32 [CX4015]  
CY8C20466A@MLF32 [CX4015]  
CY8C20467S@MLF32 [CX4015]  
CY8C20497@MLF32 [CX4015]  
CY8C20524@SSOP28 [CX1026]  
CY8C20534@SSOP28 [CX1026]  
CY8C20536A@SSOP48 [CX1028]  
CY8C20537S@SSOP48 [CX1028]  
CY8C20546@SSOP48(ISP) [CX0001]  
CY8C20547@SSOP48 [CX1028]  
CY8C20566@SSOP48 [CX1028]  
CY8C20566A@SSOP48 [CX1028]  
CY8C20567S@SSOP48 [CX1028]  
CY8C20637@MLF48 [CX4021]  
CY8C20646@QFN48 [CX4021]  
CY8C20646A@MLF48 [CX4021]  
CY8C20647S@MLF48 [CX4021]  
CY8C20666@QFN48(ISP) [CX0001]  
CY8C20667@MLF48 [CX4021]  
CY8C20747-24FDXC [BBBB]  
CY8C21123@SOIC8 [CX1045]  
CY8C21123B@SOIC8 [CX1045]  
CY8C21223@SOIC16(ISP) [CX0001]  
CY8C21234@SOIC16 [CX1016]  
CY8C21234B@SOIC16 [CX1016]  
CY8C21323@MLF24(ISP) [CX0001]  
CY8C21323@SSOP20(ISP) [CX0001]  
CY8C21323B@SSOP20 [CX1026]  
CY8C21334@SSOP20(ISP) [CX0001]  
CY8C21345@SOIC28 [CX1033]  
CY8C21434@MLF32 [CX4015]  
CY8C21434B@MLF32 [CX4015]  
CY8C21534@SSOP28(ISP) [CX0001]  
CY8C21634@MLF32 [CX4015]  
CY8C21634B@MLF32 [CX4015]  
CY8C22345@SSOP28 [CX1026]  
CY8C24123 [CX0001]  
CY8C24123@SOIC8 [CX1016]  
CY8C24123A [CX0001]  
CY8C24123A@SOIC8 [CX1016]  
CY8C24223 [CX0001]  
CY8C24223@SOIC20 [CX1033]  
CY8C24223@SSOP20 [CX1026]  
CY8C24223A [CX0001]  
CY8C24223A@SOIC20 [CX1033]  
CY8C24223A@SSOP20 [CX1026]  
CY8C24423 [CX0001]  
CY8C24423@MLF32 [CX4015]  
CY8C24423@SOIC28 [CX1033]  
CY8C24423@SSOP28 [CX1026]  
CY8C24423A [CX0001]  
CY8C24423A@MLF32 [CX4015]  
CY8C24423A@SOIC28 [CX1033]  
CY8C24423A@SSOP28 [CX1026]

CY8C24423A@SSOP28(ISP) [CX0001]  
CY8C24533(ISP) [CX0001]  
CY8C24533@SOIC28(ISP) [CX0001]  
CY8C24533@SSOP28(ISP) [CX0001]  
CY8C24533A(ISP) [CX0001]  
CY8C24533A@SOIC28(ISP) [CX0001]  
CY8C24533A@SSOP28(ISP) [CX0001]  
CY8C24533C@SOIC28 [CX1033]  
CY8C24633 [CX0001]  
CY8C24633@SOIC28 [CX1033]  
CY8C24633@SSOP28 [CX1026]  
CY8C24633A [CX0001]  
CY8C24633A@SOIC28 [CX1033]  
CY8C24633A@SSOP28 [CX1026]  
CY8C24633C [CX0001]  
CY8C24633C@SSOP28 [CX1026]  
CY8C24794@MLF56(ISP) [CX0001]  
CY8C24894@MLF56(ISP) [CX0001]  
CY8C24994@MLF68(ISP) [CX0001]  
CY8C25122(ISP) [CX0001]  
CY8C25122C(ISP) [CX0001]  
CY8C26233(ISP) [CX0001]  
CY8C26233@SOIC20(ISP) [CX0001]  
CY8C26233@SSOP20(ISP) [CX0001]  
CY8C26233C(ISP) [CX0001]  
CY8C26233C@SOIC20(ISP) [CX0001]  
CY8C26233C@SSOP20(ISP) [CX0001]  
CY8C26443(ISP) [CX0001]  
CY8C26443@SOIC28(ISP) [CX0001]  
CY8C26443@SSOP28(ISP) [CX0001]  
CY8C26443C(ISP) [CX0001]  
CY8C26443C@SOIC28(ISP) [CX0001]  
CY8C26443C@SSOP28(ISP) [CX0001]  
CY8C26643(ISP) [CX0001]  
CY8C26643@SSOP48(ISP) [CX0001]  
CY8C26643@TQFP44(ISP) [CX0001]  
CY8C26643C(ISP) [CX0001]  
CY8C26643C@SSOP48(ISP) [CX0001]  
CY8C26643C@TQFP44(ISP) [CX0001]  
CY8C27143(ISP) [CX0001]  
CY8C27243(ISP) [CX0001]  
CY8C27243@SOIC20(ISP) [CX0001]  
CY8C27243@SSOP20(ISP) [CX0001]  
CY8C27443(ISP) [CX0001]  
CY8C27443@SOIC28(ISP) [CX0001]  
CY8C27443@SSOP28(ISP) [CX0001]  
CY8C27466(ISP) [CX0001]  
CY8C27466@SSOP28(ISP) [CX0001]  
CY8C27543@TQFP44(ISP) [CX0001]  
CY8C27566@TQFP44(ISP) [CX0001]  
CY8C27643@MLF48(ISP) [CX0001]  
CY8C27643@SSOP48(ISP) [CX0001]  
CY8C27666@MLF48(ISP) [CX0001]  
CY8C27666@SSOP48(ISP) [CX0001]  
CY8C27866@TQFP100(ISP) [CX0001]  
CY8C29466(ISP) [CX0001]  
CY8C29466@SSOP28(ISP) [CX0001]  
CY8C29566@TQFP44(ISP) [CX0001]  
CY8C29666@MLF48(ISP) [CX0001]

CY8C24533 [CX0001]  
CY8C24533@SOIC28 [CX1033]  
CY8C24533@SSOP28 [CX1026]  
CY8C24533A [CX0001]  
CY8C24533A@SOIC28 [CX1033]  
CY8C24533A@SSOP28 [CX1026]  
CY8C24533C [CX0001]  
CY8C24533C@SSOP28 [CX1026]  
CY8C24633(ISP) [CX0001]  
CY8C24633@SOIC28(ISP) [CX0001]  
CY8C24633@SSOP28(ISP) [CX0001]  
CY8C24633A(ISP) [CX0001]  
CY8C24633A@SOIC28(ISP) [CX0001]  
CY8C24633A@SSOP28(ISP) [CX0001]  
CY8C24633C@SOIC28 [CX1033]  
CY8C24794@MLF56 [CX4022]  
CY8C24894@MLF56 [CX4022]  
CY8C24994@MLF68 [CX4028]  
CY8C25122 [CX0001]  
CY8C25122C [CX0001]  
CY8C26233 [CX0001]  
CY8C26233@SOIC20 [CX1033]  
CY8C26233@SSOP20 [CX1026]  
CY8C26233C [CX0001]  
CY8C26233C@SOIC20 [CX1033]  
CY8C26233C@SSOP20 [CX1026]  
CY8C26443 [CX0001]  
CY8C26443@SOIC28 [CX1033]  
CY8C26443@SSOP28 [CX1026]  
CY8C26443C [CX0001]  
CY8C26443C@SOIC28 [CX1033]  
CY8C26443C@SSOP28 [CX1026]  
CY8C26643 [CX0001]  
CY8C26643@SSOP48 [CX1028]  
CY8C26643@TQFP44 [CX3003]  
CY8C26643C [CX0001]  
CY8C26643C@SSOP48 [CX1028]  
CY8C26643C@TQFP44 [CX3003]  
CY8C27143 [CX0001]  
CY8C27243 [CX0001]  
CY8C27243@SOIC20 [CX1033]  
CY8C27243@SSOP20 [CX1026]  
CY8C27443 [CX0001]  
CY8C27443@SOIC28 [CX1033]  
CY8C27443@SSOP28 [CX1026]  
CY8C27466 [CX0001]  
CY8C27466@SSOP28 [CX1026]  
CY8C27543@TQFP44 [CX3005]  
CY8C27566@TQFP44 [CX3005]  
CY8C27643@MLF48 [CX4021]  
CY8C27643@SSOP48 [CX1028]  
CY8C27666@MLF48 [CX4021]  
CY8C27666@SSOP48 [CX1028]  
CY8C27866@TQFP100 [CX3005]  
CY8C29466 [CX0001]  
CY8C29466@SSOP28 [CX1026]  
CY8C29566@TQFP44 [CX3005]  
CY8C29666@MLF48 [CX4021]  
CY8C29666@SSOP48 [CX1028]

CY8C29666@SSOP48(ISP) [CX0001]      CY8C29866@TQFP100 [CX3043]  
CY8C29866@TQFP100(ISP) [CX0001]      CY8CLED04@QFN68 [CX4026]  
CY8CLED04@QFN68(ISP) [CX0001]      CY8CLED08@QFN48 [CX4021]  
CY8CLED08@QFN48(ISP) [CX0001]      CY8CLED08@SSOP28 [CX1026]  
CY8CLED08@SSOP28(ISP) [CX0001]      CY8CLED08@SSOP48 [CX1028]  
CY8CLED08@SSOP48(ISP) [CX0001]      CY8CLED16@QFN48 [CX4021]  
CY8CLED16@QFN48(ISP) [CX0001]      CY8CLED16@SSOP28 [CX1026]  
CY8CLED16@SSOP28(ISP) [CX0001]      CY8CLED16@SSOP48 [CX1028]  
CY8CLED16@SSOP48(ISP) [CX0001]      CY8CNP102B@LQFP100 [CX3021]  
CY8CNP102E@LQFP100 [CX3021]      CY8CTMA110@QFN32 [CX4015]  
CY8CTMA120@QFN56 [CX4022]      CY8CTMA140@QFN36 [CX4042]  
CY8CTMA140@QFN48 [CX4043]      CY8CTMA140E@QFN36 [CX4042]  
CY8CTMA140E@QFN48 [CX4043]      CY8CTMA300@QFN36 [CX4042]  
CY8CTMA300@QFN48 [CX4043]      CY8CTMA300E@QFN36 [CX4042]  
CY8CTMA300E@QFN48 [CX4043]      CY8CTMA300E-BCSP [CX0001]  
CY8CTMA301@QFN36 [CX4042]      CY8CTMA301@QFN48 [CX4043]  
CY8CTMA301E@QFN36 [CX4042]      CY8CTMA301E@QFN48 [CX4043]  
CY8CTMA340@QFN36 [CX4042]      CY8CTMA340@QFN48 [CX4043]  
CY8CTMA340E@QFN36 [CX4042]      CY8CTMA340E@QFN48 [CX4043]  
CY8CTMA341@QFN36 [CX4042]      CY8CTMA341@QFN48 [CX4043]  
CY8CTMA341E@QFN36 [CX4042]      CY8CTMA341E@QFN48 [CX4043]  
CY8CTMA375@QFN36 [CX4042]      CY8CTMA375@QFN48 [CX4043]  
CY8CTMA375E@QFN36 [CX4042]      CY8CTMA375E@QFN48 [CX4043]  
CY8CTMD200@QFN16 [CX4008]      CY8CTMD200@QFN24 [CX4012]  
CY8CTMD200@QFN32 [CX4015]      CY8CTMD200@QFN48 [CX4021]  
CY8CTMD200@SSOP48 [CX1028]      CY8CTMD200A@QFN16 [CX4008]  
CY8CTMD200A@QFN24 [CX4012]      CY8CTMD200A@QFN32 [CX4015]  
CY8CTMD200A@QFN48 [CX4021]      CY8CTMD200A@SSOP48 [CX1028]  
CY8CTMD201@QFN16 [CX4008]      CY8CTMD201@QFN24 [CX4012]  
CY8CTMD201@QFN32 [CX4015]      CY8CTMD201@QFN48 [CX4021]  
CY8CTMD201@SSOP48 [CX1028]      CY8CTMD201A@QFN16 [CX4008]  
CY8CTMD201A@QFN24 [CX4012]      CY8CTMD201A@QFN32 [CX4015]  
CY8CTMD201A@QFN48 [CX4021]      CY8CTMD201A@SSOP48 [CX1028]  
CY8CTMG110@QFN32 [CX4015]      CY8CTMG120@QFN56 [CX4022]  
CY8CTMG200 [CX0001]      CY8CTMG200@QFN16 [CX4008]  
CY8CTMG200@QFN24 [CX4012]      CY8CTMG200@QFN32 [CX4015]  
CY8CTMG200@QFN48 [CX4021]      CY8CTMG200@SSOP48 [CX1028]  
CY8CTMG200A [CX0001]      CY8CTMG200A@QFN16 [CX4008]  
CY8CTMG200A@QFN24 [CX4012]      CY8CTMG200A@QFN32 [CX4015]  
CY8CTMG200A@QFN48 [CX4021]      CY8CTMG200A@SSOP48 [CX1028]  
CY8CTMG201 [CX0001]      CY8CTMG201@QFN16 [CX4008]  
CY8CTMG201@QFN24 [CX4012]      CY8CTMG201@QFN32 [CX4015]  
CY8CTMG201@QFN48 [CX4021]      CY8CTMG201@SSOP48 [CX1028]  
CY8CTMG201A [CX0001]      CY8CTMG201A@QFN16 [CX4008]  
CY8CTMG201A@QFN24 [CX4012]      CY8CTMG201A@QFN32 [CX4015]  
CY8CTMG201A@QFN48 [CX4021]      CY8CTMG201A@SSOP48 [CX1028]  
CY8CTMG240 [CX0001]      CY8CTMG240@QFN16 [CX4008]  
CY8CTMG240@QFN24 [CX4012]      CY8CTMG240@QFN32 [CX4015]  
CY8CTMG240@QFN48 [CX4021]      CY8CTMG240@SSOP48 [CX1028]  
CY8CTMG240A [CX0001]      CY8CTMG240A@QFN16 [CX4008]  
CY8CTMG240A@QFN24 [CX4012]      CY8CTMG240A@QFN32 [CX4015]  
CY8CTMG240A@QFN48 [CX4021]      CY8CTMG240A@SSOP48 [CX1028]  
CY8CTMG300@QFN36 [CX4042]      CY8CTMG300@QFN48 [CX4043]  
CY8CTMG300E@QFN36 [CX4042]      CY8CTMG300E@QFN48 [CX4043]  
CY8CTMG301@QFN36 [CX4042]      CY8CTMG301@QFN48 [CX4043]  
CY8CTMG301E@QFN36 [CX4042]      CY8CTMG301E@QFN48 [CX4043]  
CY8CTMG340@QFN36 [CX4042]      CY8CTMG340@QFN48 [CX4043]  
CY8CTMG340E@QFN36 [CX4042]      CY8CTMG340E@QFN48 [CX4043]  
CY8CTMG341@QFN36 [CX4042]      CY8CTMG341@QFN48 [CX4043]

CY8CTMG341E@QFN36 [CX4042]	CY8CTMG341E@QFN48 [CX4043]
CY8CTST110@QFN32 [CX4015]	CY8CTST120@QFN56 [CX4022]
CY8CTST200@QFN16 [CX4008]	CY8CTST200@QFN24 [CX4012]
CY8CTST200@QFN32 [CX4015]	CY8CTST200@QFN48 [CX4021]
CY8CTST200@SSOP48 [CX1028]	CY8CTST200A@QFN16 [CX4008]
CY8CTST200A@QFN24 [CX4012]	CY8CTST200A@QFN32 [CX4015]
CY8CTST200A@QFN48 [CX4021]	CY8CTST200A@SSOP48 [CX1028]
CY8CTST201@QFN16 [CX4008]	CY8CTST201@QFN24 [CX4012]
CY8CTST201@QFN32 [CX4015]	CY8CTST201@QFN48 [CX4021]
CY8CTST201@SSOP48 [CX1028]	CY8CTST201A@QFN16 [CX4008]
CY8CTST201A@QFN24 [CX4012]	CY8CTST201A@QFN32 [CX4015]
CY8CTST201A@QFN48 [CX4021]	CY8CTST201A@SSOP48 [CX1028]
CY8CTST240@QFN16 [CX4008]	CY8CTST240@QFN24 [CX4012]
CY8CTST240@QFN32 [CX4015]	CY8CTST240@QFN48 [CX4021]
CY8CTST240@SSOP48 [CX1028]	CY8CTST240A@QFN16 [CX4008]
CY8CTST240A@QFN24 [CX4012]	CY8CTST240A@QFN32 [CX4015]
CY8CTST240A@QFN48 [CX4021]	CY8CTST240A@SSOP48 [CX1028]
CY8CTST241 [CX0001]	CY8CTST241@QFN16 [CX4008]
CY8CTST241@QFN24 [CX4012]	CY8CTST241@QFN32 [CX4015]
CY8CTST241@QFN48 [CX4021]	CY8CTST241@SSOP48 [CX1028]
CY8CTST241A [CX0001]	CY8CTST241A@QFN16 [CX4008]
CY8CTST241A@QFN24 [CX4012]	CY8CTST241A@QFN32 [CX4015]
CY8CTST241A@QFN48 [CX4021]	CY8CTST241A@SSOP48 [CX1028]
CY8CTST242 [CX0001]	CY8CTST242@QFN16 [CX4008]
CY8CTST242@QFN24 [CX4012]	CY8CTST242@QFN32 [CX4015]
CY8CTST242@QFN48 [CX4021]	CY8CTST242@SSOP48 [CX1028]
CY8CTST242A [CX0001]	CY8CTST242A@QFN16 [CX4008]
CY8CTST242A@QFN24 [CX4012]	CY8CTST242A@QFN32 [CX4015]
CY8CTST242A@QFN48 [CX4021]	CY8CTST242A@SSOP48 [CX1028]
CY8CTST300@QFN36 [CX4042]	CY8CTST300@QFN48 [CX4043]
CY8CTST300E@QFN36 [CX4042]	CY8CTST300E@QFN48 [CX4043]
CY8CTST301@QFN36 [CX4042]	CY8CTST301@QFN48 [CX4043]
CY8CTST301E@QFN36 [CX4042]	CY8CTST301E@QFN48 [CX4043]
CY8CTST340@QFN36 [CX4042]	CY8CTST340@QFN48 [CX4043]
CY8CTST340E@QFN36 [CX4042]	CY8CTST340E@QFN48 [CX4043]
CY8CTST341@QFN36 [CX4042]	CY8CTST341@QFN48 [CX4043]
CY8CTST341E@QFN36 [CX4042]	CY8CTST341E@QFN48 [CX4043]
CYRF69103@QFN40 [CX4017]	CYRF69103@QFN40 (ISP) [CX0001]
CYRF69103C@QFN40 [CX4017]	CYRF69103C@QFN40 (ISP) [CX0001]
CYRF69213@QFN40 [CX4017]	CYRF69213@QFN40 (ISP) [CX0001]
CYRF69213C@QFN40 [CX4017]	CYRF69213C@QFN40 (ISP) [CX0001]
wzt7C63813 [CX0001]	wzt7C63813@SOIC18 [CX1033]

## CYROD

### MICROCONTROLLER

CRD89C4051 [CX0001]	CRD89C4051@SOIC20 [CX1031]
CRD89C51 [CX0001]	CRD89C51@PLCC44 [CX2044]
CRD89C51@TQFP44 [CX3002]	CRD89C512RD [CX0001]
CRD89C512RD@PLCC44 [CX2044]	CRD89C512RD@TQFP44 [CX3002]
CRD89C51AA [CX0001]	CRD89C51AA@PLCC44 [CX2044]
CRD89C51AA@TQFP44 [CX3002]	CRD89C51AA1TB [CX0001]
CRD89C51AA1TB@PLCC44 [CX2044]	CRD89C51AA1TB@TQFP44 [CX3002]
CRD89C51AA1TB@TQFP48 [CX3007]	CRD89C51AB1T [CX0001]
CRD89C51AB1T@PLCC44 [CX2044]	CRD89C51AB1T@TQFP44 [CX3002]
CRD89C51AB1T@TQFP48 [CX3007]	CRD89C51AB1TA [CX0001]
CRD89C51AB1TA@PLCC44 [CX2044]	CRD89C51AB1TA@TQFP44 [CX3002]



CRD89C51AB1TA@TQFP48 [CX3007]  
CRD89C51AB1TB@PLCC44 [CX2044]  
CRD89C51AB1TB@TQFP48 [CX3007]  
CRD89C51AC1T@PLCC44 [CX2044]  
CRD89C51AC1T@TQFP48 [CX3007]  
CRD89C51AD@PLCC44 [CX2044]  
CRD89C51AD1T [CX0001]  
CRD89C51AD1T@TQFP44 [CX3002]  
CRD89C51AR1TB [CX0001]  
CRD89C51AR1TB@TQFP44 [CX3002]  
CRD89C51RA [CX0001]  
CRD89C51RA@TQFP44 [CX3002]  
CRD89C51RA2(ISP) [CX0001]  
CRD89C51RA2@PLCC44(ISP) [CX0001]  
CRD89C51RA2@TQFP44(ISP) [CX0001]  
CRD89C51RB@PLCC44 [CX2044]  
CRD89C51RB2 [CX0001]  
CRD89C51RB2@PLCC44 [CX2044]  
CRD89C51RB2@TQFP44 [CX3002]  
CRD89C51RC [CX0001]  
CRD89C51RC@TQFP44 [CX3002]  
CRD89C51RD@PLCC44 [CX2044]  
CRD89C51RE [CX0001]  
CRD89C51RE@TQFP44 [CX3002]  
CRD89C665@PLCC44 [CX2044]  
CRD89L4051 [CX0001]  
CRD89L51 [CX0001]  
CRD89L51@TQFP44 [CX3002]  
CRD89L51AA1TB@PLCC44 [CX2044]  
CRD89L51AA1TB@TQFP48 [CX3007]  
CRD89L51AB1T@PLCC44 [CX2044]  
CRD89L51AB1T@TQFP48 [CX3007]  
CRD89L51AB1TA@PLCC44 [CX2044]  
CRD89L51AB1TA@TQFP48 [CX3007]  
CRD89L51AB1TB@PLCC44 [CX2044]  
CRD89L51AB1TB@TQFP48 [CX3007]  
CRD89L51AC1T@PLCC44 [CX2044]  
CRD89L51AC1T@TQFP48 [CX3007]  
CRD89L51AD@PLCC44 [CX2044]  
CRD89L51AD1T [CX0001]  
CRD89L51AD1T@TQFP44 [CX3002]  
CRD89L51AR1TB [CX0001]  
CRD89L51AR1TB@TQFP44 [CX3002]  
CRD89L51RA [CX0001]  
CRD89L51RA@TQFP44 [CX3002]  
CRD89L51RA2(ISP) [CX0001]  
CRD89L51RA2@PLCC44(ISP) [CX0001]  
CRD89L51RA2@TQFP44(ISP) [CX0001]  
CRD89L51RB@PLCC44 [CX2044]  
CRD89L51RB2 [CX0001]  
CRD89L51RB2@PLCC44 [CX2044]  
CRD89L51RB2@TQFP44 [CX3002]  
CRD89L51RC [CX0001]  
CRD89L51RC@TQFP44 [CX3002]  
CRD89L51RD@PLCC44 [CX2044]  
CRD89L665 [CX0001]  
CRD89L665@TQFP44 [CX3002]

CRD89C51AB1TB [CX0001]  
CRD89C51AB1TB@TQFP44 [CX3002]  
CRD89C51AC1T [CX0001]  
CRD89C51AC1T@TQFP44 [CX3002]  
CRD89C51AD [CX0001]  
CRD89C51AD@TQFP44 [CX3002]  
CRD89C51AD1T@PLCC44 [CX2044]  
CRD89C51AD1T@TQFP48 [CX3007]  
CRD89C51AR1TB@PLCC44 [CX2044]  
CRD89C51AR1TB@TQFP48 [CX3007]  
CRD89C51RA@PLCC44 [CX2044]  
CRD89C51RA2 [CX0001]  
CRD89C51RA2@PLCC44 [CX2044]  
CRD89C51RA2@TQFP44 [CX3002]  
CRD89C51RB [CX0001]  
CRD89C51RB@TQFP44 [CX3002]  
CRD89C51RB2(ISP) [CX0001]  
CRD89C51RB2@PLCC44(ISP) [CX0001]  
CRD89C51RB2@TQFP44(ISP) [CX0001]  
CRD89C51RC@PLCC44 [CX2044]  
CRD89C51RD [CX0001]  
CRD89C51RD@TQFP44 [CX3002]  
CRD89C51RE@PLCC44 [CX2044]  
CRD89C665 [CX0001]  
CRD89C665@TQFP44 [CX3002]  
CRD89L4051@SOIC20 [CX1031]  
CRD89L51@PLCC44 [CX2044]  
CRD89L51AA1TB [CX0001]  
CRD89L51AA1TB@TQFP44 [CX3002]  
CRD89L51AB1T [CX0001]  
CRD89L51AB1T@TQFP44 [CX3002]  
CRD89L51AB1TA [CX0001]  
CRD89L51AB1TA@TQFP44 [CX3002]  
CRD89L51AB1TB [CX0001]  
CRD89L51AB1TB@TQFP44 [CX3002]  
CRD89L51AC1T [CX0001]  
CRD89L51AC1T@TQFP44 [CX3002]  
CRD89L51AD [CX0001]  
CRD89L51AD@TQFP44 [CX3002]  
CRD89L51AD1T@PLCC44 [CX2044]  
CRD89L51AD1T@TQFP48 [CX3007]  
CRD89L51AR1TB@PLCC44 [CX2044]  
CRD89L51AR1TB@TQFP48 [CX3007]  
CRD89L51RA@PLCC44 [CX2044]  
CRD89L51RA2 [CX0001]  
CRD89L51RA2@PLCC44 [CX2044]  
CRD89L51RA2@TQFP44 [CX3002]  
CRD89L51RB [CX0001]  
CRD89L51RB@TQFP44 [CX3002]  
CRD89L51RB2(ISP) [CX0001]  
CRD89L51RB2@PLCC44(ISP) [CX0001]  
CRD89L51RB2@TQFP44(ISP) [CX0001]  
CRD89L51RC@PLCC44 [CX2044]  
CRD89L51RD [CX0001]  
CRD89L51RD@TQFP44 [CX3002]  
CRD89L665@PLCC44 [CX2044]

# DALLAS

## E (E) PROM/FRAM/NVRAM

DS1073M-100 [CX0001]	DS1073M-60 [CX0001]
DS1073M-66 [CX0001]	DS1073M-80 [CX0001]
DS1073Z-100@SOIC8 [CX1045]	DS1073Z-60@SOIC8 [CX1045]
DS1073Z-66@SOIC8 [CX1045]	DS1073Z-80@SOIC8 [CX1045]
DS1077LU-100 [CX0001]	DS1077LU-120 [CX0001]
DS1077LU-125 [CX0001]	DS1077LU-133 [CX0001]
DS1077LU-40 [CX0001]	DS1077LU-50 [CX0001]
DS1077LU-60 [CX0001]	DS1077LU-66 [CX0001]
DS1077LZ-100 [CX1045]	DS1077LZ-120 [CX1045]
DS1077LZ-125 [CX1045]	DS1077LZ-133 [CX1045]
DS1077LZ-40@SOIC8 [CX1045]	DS1077LZ-50@SOIC8 [CX1045]
DS1077LZ-60@SOIC8 [CX1045]	DS1077LZ-66@SOIC8 [CX1045]
DS1077U-100 [CX0001]	DS1077U-120 [CX0001]
DS1077U-125 [CX0001]	DS1077U-133 [CX0001]
DS1077U-40 [CX0001]	DS1077U-50 [CX0001]
DS1077U-60 [CX0001]	DS1077U-66 [CX0001]
DS1077Z-100 [CX1045]	DS1077Z-120 [CX1045]
DS1077Z-125 [CX1045]	DS1077Z-133 [CX1045]
DS1077Z-40@SOIC8 [CX1045]	DS1077Z-50@SOIC8 [CX1045]
DS1077Z-60@SOIC8 [CX1045]	DS1077Z-66@SOIC8 [CX1045]
DS1086U [CX0001]	DS1086Z [CX1045]
DS1220AB [CX0001]	DS1220AD [CX0001]
DS1220Y [CX0001]	DS1225AB [CX0001]
DS1225AD [CX0001]	DS1225D [CX0001]
DS1225E [CX0001]	DS1225Y [CX0001]
DS1230AB [CX0001]	DS1230ABP [CX2068]
DS1230W [CX0001]	DS1230Y [CX0001]
DS1230YP [CX2068]	DS1235AB [CX0001]
DS1235Y [CX0001]	DS1243Y [CX0001]
DS1244 [CX0001]	DS1244P [CX2068]
DS1244Y [CX0001]	DS1244YP [CX2068]
DS1245AB [CX0001]	DS1245EE [CX0001]
DS1245P [CX2068]	DS1245W [CX0001]
DS1245Y [CX0001]	DS1248P [CX2068]
DS1248W [CX0001]	DS1248Y [CX0001]
DS1249AB [CX0001]	DS1249W [CX0001]
DS1249Y [CX0001]	DS1250AB [CX0001]
DS1250ABP [CX2068]	DS1250W [CX0001]
DS1250Y [CX0001]	DS1250YP [CX2068]
DS1251AB [CX0001]	DS1251P [CX2068]
DS1251W [CX0001]	DS1251Y [CX0001]
DS1256P [CX2068]	DS1256W [CX0001]
DS1256Y [CX0001]	DS1258AB [CX0001]
DS1258W [CX0001]	DS1258Y [CX0001]
DS1265AB [CX0001]	DS1265W [CX0001]
DS1265Y [CX0001]	DS1270AB [CX0001]
DS1270W [CX0001]	DS1270Y [CX0001]
DS1284 [CX0001]	DS1284N [CX0001]
DS1284Q@PLCC28 [CX2028]	DS1284QN@PLCC28 [CX2028]
DS1286 [CX0001]	DS1286I [CX0001]
DS1287 [CX0001]	DS1287A [CX0001]
DS12887 [CX0001]	DS12887A [CX0001]
DS12C887 [CX0001]	DS12C887+ [CX0001]
DS12C887A [CX0001]	DS1330AB [CX0001]
DS1330ABP [CX2068]	DS1330WP [CX2068]

DS1330Y [CX0001]	DS1330YP [CX2068]
DS1345AB [CX0001]	DS1345P [CX2068]
DS1345W [CX0001]	DS1345Y [CX0001]
DS1350AB [CX0001]	DS1350P [CX2068]
DS1350W [CX0001]	DS1350Y [CX0001]
DS1385 [CX0001]	DS1386(32K) [CX0001]
DS1386(8K) [CX0001]	DS1387 [CX0001]
DS14285 [CX0001]	DS14287 [CX0001]
DS1485 [CX0001]	DS1485@SOIC28 [CX1035]
DS1486 [CX0001]	DS1486P [CX2068]
DS1488 [CX0001]	DS1501 [CX0001]
DS1511 [CX0001]	DS1553 [CX0001]
DS1553P [CX2068]	DS1553W [CX0001]
DS1553WP [CX2068]	DS1554 [CX0001]
DS1554W [CX0001]	DS1556 [CX0001]
DS1630AB [CX0001]	DS1630ABL [CX2068]
DS1630Y [CX0001]	DS1630YL [CX2068]
DS1642 [CX0001]	DS1643 [CX0001]
DS1643P [CX2068]	DS1644 [CX0001]
DS1644P [CX2068]	DS1644PS [CX2068]
DS1645AB [CX0001]	DS1645ABP [CX2068]
DS1645EE [CX0001]	DS1645Y [CX0001]
DS1645YP [CX2068]	DS1646 [CX0001]
DS1646P [CX2068]	DS1647 [CX0001]
DS1647LPM [CX2068]	DS1650AB [CX0001]
DS1650ABP [CX2068]	DS1650Y [CX2068]
DS1650YP [CX0001]	DS1685-3 [CX0001]
DS1685-3@SOP24 [CX1033]	DS1685-5 [CX0001]
DS1685-5@SOP24 [CX1033]	DS1687-3 [CX0001]
DS1687-5 [CX0001]	DS17287-3 [CX0001]
DS17287-5 [CX0001]	DS1742 [CX0001]
DS1742W [CX0001]	DS1743 [CX0001]
DS1743P [CX2068]	DS1743W [CX0001]
DS1743WP [CX2068]	DS1744 [CX0001]
DS1744P [CX2068]	DS1744W [CX0001]
DS1744WP [CX2068]	DS1746 [CX0001]
DS1746P [CX2068]	DS1747 [CX0001]
DS1747P [CX2068]	DS1747PS [CX2068]
DS1747W [CX0001]	DS1747WP [CX2068]
DS1747WPS [CX2068]	DS17487-3 [CX0001]
DS17487-5 [CX0001]	DS17887-3 [CX0001]
DS17887-5 [CX0001]	DS2406@TO-92 [CX0001]
DS2406P@TSOC6 [CX1066]	DS2430A@TO-92 [CX0001]
DS2430AP@TSOC6 [CX1066]	DS2431@TO-92 [CX0001]
DS2431P@TSOC6 [CX1066]	DS2432P@TSOC6 [CX1066]
DS2433@PR-35 [CX0001]	DS2433S(3.9)@SOIC8 [CX1045]
DS2433S(5.5)@SOIC8 [CX1044]	DS2502 [CX0001]
DS2502P@TSOC6 [CX1066]	DS2502S@SOIC8 [CX1045]
DS2502UNW [CX0001]	DS2502UNW@SOIC8 [CX1045]
DS2502UNW@SOT-23 [CX1041]	DS2502UNW@TSOC6 [CX1066]
DS2505 [CX0001]	DS2505S@TSOC6 [CX1066]
DS2506 [CX0001]	DS2506S@SOIC8 [CX1044]
DS4510@uSOP10 [CX1016]	DS4520@TSSOP16 [CX1000]
DS4550@TSSOP20 [CX1000]	

#### MICROCONTROLLER

DS5000[32K] [CX0001]	DS5000[8K] [CX0001]
DS5000T[32K] [CX0001]	DS5000T[8K] [CX0001]

DS87C520 [CX0001]  
DS87C520@TQFP44 [CX3003]  
DS89C420 (rev.A) [CX0001]  
DS89C420 (rev.A)@TQFP44 [CX3003]  
DS89C420@TQFP44 [CX3003]  
DS89C430@PLCC44 [CX2044]  
DS89C440 [CX0001]  
DS89C440@TQFP44 [CX3003]  
DS89C450@PLCC44 [CX2044]

DS87C520@PLCC44 [CX2044]  
DS89C420 [CX0001]  
DS89C420 (rev.A)@PLCC44 [CX2044]  
DS89C420@PLCC44 [CX2044]  
DS89C430 [CX0001]  
DS89C430@TQFP44 [CX3003]  
DS89C440@PLCC44 [CX2044]  
DS89C450 [CX0001]  
DS89C450@TQFP44 [CX3003]

## DENSE-PAC

### E (E) PROM/FRAM/NVRAM

DPV27C101 [CX0001]  
DPV27C256 [CX0001]  
DPV27C512 [CX0001]

DPV27C101@PLCC32 [CX2032]  
DPV27C256@PLCC32 [CX2032]  
DPV27C512@PLCC32 [CX2032]

## DEUTRON

### E (E) PROM/FRAM/NVRAM

AC25LV010 [CX0001]  
AC25LV512 [CX0001]  
P439LV010@PLCC32 [CX2032]  
P439LV040@PLCC32 [CX2032]  
P439LV088@TSOP48 [CX1004]

AC25LV010@SOIC8 [CX1045#1]  
AC25LV512@SOIC8 [CX1045#1]  
P439LV010@VSOP32 [CX1003]  
P439LV040@VSOP32 [CX1003]  
P439VF800@TSOP48 [CX1004]

## E-CMOS

### E (E) PROM/FRAM/NVRAM

EC24C01 [CX0001]  
EC24C01@SOIC8 [CX1045]  
EC24C02 [CX0001]  
EC24C02@SOIC8 [CX1045]  
EC24C02A [CX0001]  
EC24C02A@SOIC8 [CX1045]  
EC24C04 [CX0001]  
EC24C04@SOIC8 [CX1045]  
EC24C04A [CX0001]  
EC24C04A@SOIC8 [CX1045]  
EC24C08 [CX0001]  
EC24C08@SOIC8 [CX1045]  
EC24C08A [CX0001]  
EC24C08A@SOIC8 [CX1045]  
EC24C128 [CX0001]  
EC24C128@SOIC8 [CX1045]  
EC24C16 [CX0001]  
EC24C16@SOIC8 [CX1045]  
EC24C16A [CX0001]  
EC24C16A@SOIC8 [CX1045]  
EC24C256 [CX0001]  
EC24C256@SOIC8 [CX1045]  
EC24C32 [CX0001]  
EC24C32@SOIC8 [CX1045]

EC24C01@DFN8 [CX4002]  
EC24C01@TSSOP8 [CX1059]  
EC24C02@DFN8 [CX4002]  
EC24C02@TSSOP8 [CX1059]  
EC24C02A@DFN8 [CX4002]  
EC24C02A@TSSOP8 [CX1059]  
EC24C04@DFN8 [CX4002]  
EC24C04@TSSOP8 [CX1059]  
EC24C04A@DFN8 [CX4002]  
EC24C04A@TSSOP8 [CX1059]  
EC24C08@DFN8 [CX4002]  
EC24C08@TSSOP8 [CX1059]  
EC24C08A@DFN8 [CX4002]  
EC24C08A@TSSOP8 [CX1059]  
EC24C128@DFN8 [CX4002]  
EC24C128@TSSOP8 [CX1059]  
EC24C16@DFN8 [CX4002]  
EC24C16@TSSOP8 [CX1059]  
EC24C16A@DFN8 [CX4002]  
EC24C16A@TSSOP8 [CX1059]  
EC24C256@DFN8 [CX4002]  
EC24C256@TSSOP8 [CX1059]  
EC24C32@DFN8 [CX4002]  
EC24C32@TSSOP8 [CX1059]

EC24C64 [CX0001]  
EC24C64@SOIC8 [CX1045]

EC24C64@DFN8 [CX4002]  
EC24C64@TSSOP8 [CX1059]

## EETI

### MICROCONTROLLER

PCAP7800@QFN32 [CX4015]

PCAP7800@QFN48 [CX4043]

## EFST

### E (E) PROM/FRAM/NVRAM

EM25LV010@SOIC8 [CX1045]  
EM25LV512@SOIC8 [CX1045]  
F49B002UA [CX0001]  
F49L004BA@PLCC32 [CX2032]  
F49L004UA@PLCC32 [CX2032]  
F49L040A@PLCC32 [CX2032]  
F49L160BA@TSOP48 [CX1004]  
F49L400BA@TSOP48 [CX1004]  
F49L800BA@TSOP48 [CX1004]

EM25LV010@VFQFPN8 [CX4006]  
EM25LV512@VFQFPN8 [CX4006]  
F49B002UA@PLCC32 [CX2032]  
F49L004BA@TSOP40 [CX1006]  
F49L004UA@TSOP40 [CX1006]  
F49L040A@VSOP32 [CX1003]  
F49L160UA@TSOP48 [CX1004]  
F49L400UA@TSOP48 [CX1004]  
F49L800UA@TSOP48 [CX1004]

## eGalax

### MICROCONTROLLER

PCAP7800@QFN32 [CX4015]

PCAP7800@QFN48 [CX4043]

## ELECTRONIC ARRAYS

### E (E) PROM/FRAM/NVRAM

EA2716 [CX0001]

## EM

### MICROCONTROLLER

EM6580@SOIC8 [CX1045]

EM68128@TSSOP24 [CX1000]

## EMTC

### E (E) PROM/FRAM/NVRAM

EM24C02 [CX0001]  
EM24C02@TSSOP8 [CX1059]  
EM24C04@SOIC8 [CX1045]  
EM24C08 [CX0001]  
EM24C08@TSSOP8 [CX1059]  
EM24C16@SOIC8 [CX1045]  
EM25SL512@SOIC8 [CX1045]  
EM29SF002AB@PLCC32 [CX2032]

EM24C02@SOIC8 [CX1045]  
EM24C04 [CX0001]  
EM24C04@TSSOP8 [CX1059]  
EM24C08@SOIC8 [CX1045]  
EM24C16 [CX0001]  
EM24C16@TSSOP8 [CX1059]  
EM29SF002AB [CX0001]  
EM29SF002AB@TSOP32 [CX1002]

EM29SF002AT [CX0001]  
EM29SF002AT@TSOP32 [CX1002]  
EM29SF002NAB@PLCC32 [CX2032]  
EM29SF002NAT [CX0001]  
EM29SF002NAT@TSOP32 [CX1002]

EM29SF002AT@PLCC32 [CX2032]  
EM29SF002NAB [CX0001]  
EM29SF002NAB@TSOP32 [CX1002]  
EM29SF002NAT@PLCC32 [CX2032]

## ENERGY

### MICROCONTROLLER

EFM32TG108F16@QFN24 [CX4034-1]      EFM32TG108F32@QFN24 [CX4034-1]  
EFM32TG108F4@QFN24 [CX4034-1]      EFM32TG108F8@QFN24 [CX4034-1]  
EFM32TG110F16@QFN24 [CX4034-1]      EFM32TG110F32@QFN24 [CX4034-1]  
EFM32TG110F4@QFN24 [CX4034-1]      EFM32TG110F8@QFN24 [CX4034-1]  
EFM32TG210F16@QFN32 [CX4086-1]      EFM32TG210F32@QFN32 [CX4086-1]  
EFM32TG210F8@QFN32 [CX4086-1]      EFM32TG222F16@TQFP48 [CX3007-6]  
EFM32TG222F32@TQFP48 [CX3007-6]      EFM32TG222F8@TQFP48 [CX3007-6]  
EFM32TG225F16@BGA48 [CX5237-1]      EFM32TG225F32@BGA48 [CX5237-1]  
EFM32TG225F8@BGA48 [CX5237-1]      EFM32TG230F16@QFN64 [CX4070-2]  
EFM32TG230F32@QFN64 [CX4070-2]      EFM32TG230F8@QFN64 [CX4070-2]  
EFM32TG232F16@TQFP64 [CX3011-10]      EFM32TG232F32@TQFP64 [CX3011-10]  
EFM32TG232F8@TQFP64 [CX3011-10]      EFM32TG822F16@TQFP48 [CX3007-6]  
EFM32TG822F32@TQFP48 [CX3007-6]      EFM32TG822F8@TQFP48 [CX3007-6]  
EFM32TG825F16@BGA48 [CX5237-1]      EFM32TG825F32@BGA48 [CX5237-1]  
EFM32TG825F8@BGA48 [CX5237-1]      EFM32TG840F16@QFN64 [CX4070-2]  
EFM32TG840F32@QFN64 [CX4070-2]      EFM32TG840F8@QFN64 [CX4070-2]  
EFM32TG842F16@TQFP64 [CX3011-10]      EFM32TG842F32@TQFP64 [CX3011-10]  
EFM32TG842F8@TQFP64 [CX3011-10]

## EON

### E (E) PROM/FRAM/NVRAM

EN25B05(Bottom Boot)@SOP8(4.0) [CX1045]  
EN25B05(Bottom Boot)@SOP8(5.4) [CX1044]  
EN25B05(Bottom Boot)@VDFN8 [CX4005]  
EN25B05(Top Boot)@SOP8(4.0) [CX1045]  
EN25B05(Top Boot)@SOP8(5.4) [CX1044]  
EN25B05(Top Boot)@VDFN8 [CX4005]  
EN25B10(Bottom Boot)@SOP8(4.0) [CX1045]  
EN25B10(Bottom Boot)@SOP8(5.4) [CX1044]  
EN25B10(Bottom Boot)@VDFN8 [CX4005]  
EN25B10(Top Boot)@SOP8(4.0) [CX1045]  
EN25B10(Top Boot)@SOP8(5.4) [CX1044]  
EN25B10(Top Boot)@VDFN8 [CX4005]  
EN25B16(Bottom Boot)@SOP8 [CX1044#1]  
EN25B16(Bottom Boot)@SOP8(ISP) [CX0001]  
EN25B16(Bottom Boot)@VFQFN8(ISP) [CX0001]  
EN25B16(Bottom Boot)@VFQFPN8 [CX4006#1]  
EN25B16(Top Boot)@SOP8 [CX1044#1]  
EN25B16(Top Boot)@SOP8(ISP) [CX0001]  
EN25B16(Top Boot)@VFQFN8(ISP) [CX0001]  
EN25B16(Top Boot)@VFQFPN8 [CX4006#1]  
EN25B20(Bottom Boot)@SOP8(4.0) [CX1045#1]  
EN25B20(Bottom Boot)@SOP8(5.4) [CX1044#1]  
EN25B20(Bottom Boot)@VDFN8 [CX4005#1]  
EN25B20(Top Boot)@SOP8(4.0) [CX1045#1]

EN25B20(Top Boot)@SOP8(5.4) [CX1044#1]  
EN25B20(Top Boot)@VDFN8 [CX4005#1]  
EN25B32(Bottom Boot)@SOP16 [CX1033#1]  
EN25B32(Bottom Boot)@SOP16(ISP) [CX1033#1]  
EN25B32(Bottom Boot)@SOP8 [CX1044#1]  
EN25B32(Bottom Boot)@SOP8(ISP) [CX0001]  
EN25B32(Bottom Boot)@VDFN8 [CX4006#1]  
EN25B32(Bottom Boot)@VDFN8(ISP) [CX0001]  
EN25B32(Top Boot)@SOP16 [CX1033#1]  
EN25B32(Top Boot)@SOP16(ISP) [CX1033#1]  
EN25B32(Top Boot)@SOP8 [CX1044#1]  
EN25B32(Top Boot)@SOP8(ISP) [CX0001]  
EN25B32(Top Boot)@VDFN8 [CX4006#1]  
EN25B32(Top Boot)@VDFN8(ISP) [CX0001]  
EN25B40(Bottom Boot)@SOP8(4.0) [CX1045#1]  
EN25B40(Bottom Boot)@SOP8(5.4) [CX1044#1]  
EN25B40(Bottom Boot)@VDFN8 [CX4005#1]  
EN25B40(Top Boot)@SOP8(4.0) [CX1045#1]  
EN25B40(Top Boot)@SOP8(5.4) [CX1044#1]  
EN25B40(Top Boot)@VDFN8 [CX4005#1]  
EN25B64(Bottom Boot)@SOP16 [CX1033#1]  
EN25B64(Bottom Boot)@SOP16(ISP) [CX1033#1]  
EN25B64(Bottom Boot)@VDFN8 [CX4006#1]  
EN25B64(Bottom Boot)@VDFN8(ISP) [CX0001]  
EN25B64(Top Boot)@SOP16 [CX1033#1]  
EN25B64(Top Boot)@SOP16(ISP) [CX1033#1]  
EN25B64(Top Boot)@VDFN8 [CX4006#1]  
EN25B64(Top Boot)@VDFN8(ISP) [CX0001]  
EN25B80(Bottom Boot)@SOP8(4.0) [CX1045#1]  
EN25B80(Bottom Boot)@SOP8(5.4) [CX1044#1]  
EN25B80(Bottom Boot)@VDFN8 [CX4005#1]  
EN25B80(Top Boot)@SOP8(4.0) [CX1045#1]  
EN25B80(Top Boot)@SOP8(5.4) [CX1044#1]  
EN25B80(Top Boot)@VDFN8 [CX4005#1]  
EN25D16 [CX0001] EN25D16@SOP16 [CX1033#1]  
EN25D16@SOP8 [CX1044#1] EN25D16@VDFN8 [CX4006#1]  
EN25D80 [CX0001] EN25D80@SOP8 [CX1044#1]  
EN25D80@VDFN8 [CX4005#1] EN25F05@SOP8(4.0) [CX1045#1]  
EN25F05@SOP8(5.4) [CX1044#1] EN25F05@VDFN8 [CX4005#1]  
EN25F10@SOP8(4.0) [CX1045#1] EN25F10@SOP8(5.4) [CX1044#1]  
EN25F10@VDFN8 [CX4005#1] EN25F16 [CX0001]  
EN25F16@SOP16 [CX1033#1] EN25F16@SOP8 [CX1044#1]  
EN25F16@VDFN8 [CX4006#1] EN25F20@SOP8(4.0) [CX1045#1]  
EN25F20@SOP8(5.4) [CX1044#1] EN25F20@VDFN8 [CX4005#1]  
EN25F32 [CX0001] EN25F32@SOP16 [CX1033#1]  
EN25F32@SOP8 [CX1044#1] EN25F32@VDFN8 [CX4006#1]  
EN25F40(fast mode)@SOP8(150mil) [CX1045#1]  
EN25F40(fast mode)@SOP8(200mil) [CX1044#1]  
EN25F40(fast mode)@VDFN8 [CX4005#1]  
EN25F40@SOP8(150mil) [CX1045#1] EN25F40@SOP8(200mil) [CX1044#1]  
EN25F40@VDFN8 [CX4005#1] EN25F64@DFN8 [CX4006#1]  
EN25F64@SOP16 [CX1033#1] EN25F64@SOP8 [CX1044#1]  
EN25F64@VDFN8 [CX4005#1] EN25F80 [CX0001]  
EN25F80@SOP8(4.0) [CX1045#1] EN25F80@SOP8(5.4) [CX1044#1]  
EN25F80@VDFN8 [CX4005#1] EN25LF05@SOP8(4.0) [CX1045#1]  
EN25LF05@SOP8(5.4) [CX1044#1] EN25LF05@VDFN8 [CX4005#1]  
EN25LF10@SOP8(4.0) [CX1045#1] EN25LF10@SOP8(5.4) [CX1044#1]  
EN25LF10@VDFN8 [CX4005#1] EN25LF20@SOP8 [CX1044#1]  
EN25LF20@VDFN8 [CX4005#1] EN25LF40 [CX0001]

EN25LF40@SOP8(150mil) [CX1045#1]      EN25LF40@SOP8(200mil) [CX1044#1]  
EN25LF40@VDFN8 [CX4005#1]      EN25LV010@SOIC8 [CX1045]  
EN25LV010@VFQFPN8 [CX4006]      EN25LV020@SOIC8 [CX1045#1]  
EN25LV020@VFQFPN8 [CX4006#1]      EN25LV040@SOIC8 [CX1045#1]  
EN25LV040@VFQFPN8 [CX4006#1]      EN25LV080@SOIC8 [CX1045#1]  
EN25LV080@VFQFPN8 [CX4006#1]      EN25LV160@SOIC8 [CX1045#1]  
EN25LV160@SOIC8(ISP) [CX0001]      EN25LV160@VFQFPN8 [CX4006#1]  
EN25LV160@VFQFPN8(ISP) [CX0001]      EN25LV512@SOIC8 [CX1045]  
EN25LV512@VFQFPN8 [CX4006]      EN25P05@SOP8(4.0) [CX1045]  
EN25P05@SOP8(5.4) [CX1044]      EN25P05@VDFN8 [CX4005]  
EN25P10@SOP8(4.0) [CX1045]      EN25P10@SOP8(5.4) [CX1044]  
EN25P10@VDFN8 [CX4005]      EN25P16@SOP8 [CX1044#1]  
EN25P16@SOP8(ISP) [CX0001]      EN25P16@VFQFPN8 [CX4006#1]  
EN25P16@VFQFPN8(ISP) [CX0001]      EN25P20@SOP8(4.0) [CX1045#1]  
EN25P20@SOP8(5.4) [CX1044#1]      EN25P20@VDFN8 [CX4005#1]  
EN25P32@SOP16 [CX1033#1]      EN25P32@SOP16(ISP) [CX0001]  
EN25P32@SOP8 [CX1044#1]      EN25P32@SOP8(ISP) [CX0001]  
EN25P32@VDFN8 [CX4006#1]      EN25P32@VDFN8(ISP) [CX0001]  
EN25P40@SOP8(4.0) [CX1045#1]      EN25P40@SOP8(5.4) [CX1044#1]  
EN25P40@VDFN8 [CX4005#1]      EN25P64@SOP16 [CX1033#1]  
EN25P64@SOP16(ISP) [CX1033#1]      EN25P64@VDFN8 [CX4006#1]  
EN25P64@VDFN8(ISP) [CX0001]      EN25P80@SOP8(4.0) [CX1045#1]  
EN25P80@SOP8(5.4) [CX1044#1]      EN25P80@VDFN8 [CX4005#1]  
EN25Q128A [CX0001#1]      EN25Q128A@SOP16 [CX1033#1]  
EN25Q128A@SOP8 [CX1044#1]      EN25Q128A@VDFN8 [CX4006#1]  
EN25Q128A@VSOP8 [CX1044#1]      EN25Q16 [CX0001]  
EN25Q16@SOP16 [CX1033#1]      EN25Q16@SOP8(4.0) [CX1045#1]  
EN25Q16@SOP8(5.4) [CX1044#1]      EN25Q16@VDFN8 [CX4006#1]  
EN25Q16A [CX0001]      EN25Q16A@SOP16 [CX1033#1]  
EN25Q16A@SOP8(4.0) [CX1045#1]      EN25Q16A@SOP8(5.4) [CX1044#1]  
EN25Q16A@VDFN8 [CX4006#1]      EN25Q32A [CX0001]  
EN25Q32A@SOP8 [CX1044#1]      EN25Q32A@VDFN8 [CX4005#1]  
EN25Q32B [CX0001]      EN25Q32B@SOP8 [CX1044#1]  
EN25Q32B@VDFN8 [CX4005#1]      EN25Q40@SOP8(4.0) [CX1044#1]  
EN25Q40@SOP8(5.4) [CX1045#1]      EN25Q40@VDFN8 [CX4005#1]  
EN25Q64@SOP16 [CX1033#1]      EN25Q64@SOP8 [CX1044#1]  
EN25Q64@VDFN8(5\*6mm) [CX4005#1]      EN25Q64@VDFN8(6\*8mm) [CX4006#1]  
EN25Q80A@SOP8(4.0) [CX1045#1]      EN25Q80A@SOP8(5.4) [CX1044#1]  
EN25Q80A@VDFN8 [CX4005#1]      EN25QA128@TFBGA24 [CX5146]  
EN25QA256@BGA24 [CX5146]      EN25QA64@TFBGA24 [CX5146]  
EN25QH128@SOP16 [CX1033#1]      EN25QH128@TFBGA24 [CX5146]  
EN25QH128@VDFN8 [CX4006#1]      EN25QH128A [CX0001#1]  
EN25QH128A@SOP16 [CX1033#1]      EN25QH128A@SOP8 [CX1044#1]  
EN25QH128A@TFBGA24 [CX5146]      EN25QH128A@VDFN8 [CX4006#1]  
EN25QH128A@VSOP8 [CX1044#1]      EN25QH256@SOP16 [CX1033#1]  
EN25QH256@TFBGA24 [CX5146]      EN25QH256@VDFN8 [CX4006#1]  
EN25QH64@TFBGA24 [CX5146]      EN25S10@SOP8 [CX1045#1]  
EN25S10@VDFN8 [CX4002#1]      EN25S16@SOP8 [CX1044#1]  
EN25S16@VFQFPN8 [CX4006#1]      EN25S20@SOP8 [CX1045#1]  
EN25S20@VDFN8 [CX4002#1]  
EN25S32(Bottom Boot)@SOP16 [CX1033#1]  
EN25S32(Bottom Boot)@SOP16(ISP) [CX1033#1]  
EN25S32(Bottom Boot)@SOP8 [CX1044#1]  
EN25S32(Bottom Boot)@SOP8(ISP) [CX0001]  
EN25S32(Bottom Boot)@VDFN8 [CX4006#1]  
EN25S32(Bottom Boot)@VDFN8(ISP) [CX0001]  
EN25S32(Top Boot)@SOP16 [CX1033#1]  
EN25S32(Top Boot)@SOP16(ISP) [CX1033#1]  
EN25S32(Top Boot)@SOP8 [CX1044#1]



EN25S32(Top Boot)@SOP8(ISP) [CX0001]  
EN25S32(Top Boot)@VDFN8 [CX4006#1]  
EN25S32(Top Boot)@VDFN8(ISP) [CX0001]  
EN25S32@SOP16 [CX1033#1] EN25S32@SOP8 [CX1044#1]  
EN25S32@VDFN8 [CX4006#1] EN25S32@VSOP8 [CX1044#1]  
EN25S40@SOP8 [CX1045#1] EN25S40@VDFN8(2\*3mm) [CX4002#1]  
EN25S40@VDFN8(5\*6mm) [CX4005#1] EN25S64@VDFN8 [CX4005#1]  
EN25S64@VSOP8 [CX1044#1] EN25S80@SOP8(150mil) [CX1045]  
EN25S80@SOP8(200mil) [CX1044] EN25S80@VDFN8 [CX4005]  
EN25T16@SOP8 [CX1044#1] EN25T16@VFQFPN8 [CX4006#1]  
EN25T40@SOP8(150mil) [CX1045#1] EN25T40@SOP8(209mil) [CX1044#1]  
EN25T40@VDFN8 [CX4005#1] EN25T80 [CX0001]  
EN25T80@SOP8 [CX1044#1] EN25T80@VDFN8 [CX4005#1]  
EN27C010 [CX0001] EN27C010@PLCC32 [CX2032]  
EN27C512 [CX0001] EN27C512@PLCC32  
EN27LN1G08@TSOP48 [CX1004-3] EN29F002AB [CX0001]  
EN29F002AB@PLCC32 [CX2032] EN29F002AB@TSOP32 [CX1002]  
EN29F002ANB [CX0001] EN29F002ANB@PLCC32 [CX2032]  
EN29F002ANB@TSOP32 [CX1002] EN29F002ANT [CX0001]  
EN29F002ANT@PLCC32 [CX2032] EN29F002ANT@TSOP32 [CX1002]  
EN29F002AT [CX0001] EN29F002AT@PLCC32 [CX2032]  
EN29F002AT@TSOP32 [CX1002] EN29F002B [CX0001]  
EN29F002B@PLCC32 [CX2032] EN29F002B@TSOP32 [CX1002]  
EN29F002NB [CX0001] EN29F002NB@PLCC32 [CX2032]  
EN29F002NB@TSOP32 [CX1002] EN29F002NT [CX0001]  
EN29F002NT@PLCC32 [CX2032] EN29F002NT@TSOP32 [CX1002]  
EN29F002T [CX0001] EN29F002T@PLCC32 [CX2032]  
EN29F002T@TSOP32 [CX1002] EN29F010 [CX0001]  
EN29F010@PLCC32 [CX2032] EN29F010@TSOP32 [CX1002]  
EN29F010@VSOP32 [CX1003] EN29F040 [CX0001]  
EN29F040@PLCC32 [CX2032] EN29F040@TSOP32 [CX1002]  
EN29F040A [CX0001] EN29F040A@PLCC32 [CX2032]  
EN29F040A@TSOP32 [CX1002] EN29F080@TSOP40 [CX1006]  
EN29F512 [CX0001] EN29F512@PLCC32 [CX2032]  
EN29F512@TSOP32 [CX1002] EN29F512@VSOP32 [CX1003]  
EN29F800B@TSOP48 [CX1004] EN29F800T@TSOP48 [CX1004]  
EN29LV010@PLCC32 [CX2032] EN29LV010@TSOP32 [CX1002]  
EN29LV010@VSOP32 [CX1003] EN29LV010@WFBGA34 [CX5037]  
EN29LV040@PLCC32 [CX2032] EN29LV040@TSOP32 [CX1002]  
EN29LV040@VSOP32 [CX1003] EN29LV040A [CX0001]  
EN29LV040A@PLCC32 [CX2032] EN29LV040A@TSOP32 [CX1002]  
EN29LV040A@VSOP32 [CX1003] EN29LV160AB@FBGA48 [CX5002]  
EN29LV160AB@TSOP48 [CX1004] EN29LV160AT@FBGA48 [CX5002]  
EN29LV160AT@TSOP48 [CX1004] EN29LV160B@FBGA48 [CX5002]  
EN29LV160B@TSOP48 [CX1004] EN29LV160BB@FBGA48 [CX5002]  
EN29LV160BB@TSOP48 [CX1004] EN29LV160BT@FBGA48 [CX5002]  
EN29LV160BT@TSOP48 [CX1004] EN29LV160T@FBGA48 [CX5002]  
EN29LV160T@TSOP48 [CX1004] EN29LV320AB@FBGA48 [CX5002]  
EN29LV320AB@TSOP48 [CX1004] EN29LV320AT@FBGA48 [CX5002]  
EN29LV320AT@TSOP48 [CX1004] EN29LV320B@FBGA48 [CX5002]  
EN29LV320B@TSOP48 [CX1004] EN29LV320T@FBGA48 [CX5002]  
EN29LV320T@TSOP48 [CX1004] EN29LV400AB@FBGA48 [CX5002]  
EN29LV400AB@TSOP48 [CX1004] EN29LV400AT@FBGA48 [CX5002]  
EN29LV400AT@TSOP48 [CX1004] EN29LV400B@FBGA48 [CX5002]  
EN29LV400B@TSOP48 [CX1004] EN29LV400T@FBGA48 [CX5002]  
EN29LV400T@TSOP48 [CX1004] EN29LV512@PLCC32 [CX2032]  
EN29LV512@TSOP32 [CX1002] EN29LV512@VSOP32 [CX1003]  
EN29LV640B@FBGA48 [CX5002] EN29LV640B@TSOP48 [CX1004]  
EN29LV640H@FBGA48 [CX5002] EN29LV640H@TSOP48 [CX1004]

EN29LV640L@FBGA48 [CX5002]  
EN29LV640T@FBGA48 [CX5002]  
EN29LV641H@FBGA63 [CX5041]  
EN29LV641L@FBGA63 [CX5041]  
EN29LV800AB@FBGA48 [CX5002]  
EN29LV800AT@FBGA48 [CX5002]  
EN29LV800B@TSOP48 [CX1004]  
EN29LV800BB@TSOP48 [CX1004]  
EN29LV800BT@TSOP48 [CX1004]  
EN29LV800CB@TSOP48 [CX1004]  
EN29LV800CT@TSOP48 [CX1004]  
EN29PL032@FBGA48 [CX5002]  
EN29PL032@TSOP48 [CX1004]  
EN29PL064@FBGA56 [CX5045]  
EN29SL160B@FBGA48 [CX5002]  
EN29SL160B@WFBGA48 [CX5038]  
EN29SL160T@FBGA48 [CX5002]  
EN29SL160T@WFBGA48 [CX5038]  
EN29SL400B@FBGA48 [CX5002]  
EN29SL400T@FBGA48 [CX5002]  
EN29SL800B@FBGA48 [CX5002]  
EN29SL800B@WFBGA48 [CX5038]  
EN29SL800T@FBGA48 [CX5002]  
EN29SL800T@WFBGA48 [CX5038]  
EN71PL03280@FBGA56 [CX5045]  
EN71PL064A0@FBGA56 [CX5045]  
EN71SN10E@BGA107 [CX5028]

EN29LV640L@TSOP48 [CX1004]  
EN29LV640T@TSOP48 [CX1004]  
EN29LV641H@TSOP48 [CX1004]  
EN29LV641L@TSOP48 [CX1004]  
EN29LV800AB@TSOP48 [CX1004]  
EN29LV800AT@TSOP48 [CX1004]  
EN29LV800BB@FBGA48 [CX5002]  
EN29LV800BT@FBGA48 [CX5002]  
EN29LV800CB@FBGA48 [CX5002]  
EN29LV800CT@FBGA48 [CX5002]  
EN29LV800T@TSOP48 [CX1004]  
EN29PL032@FBGA56 [CX5045]  
EN29PL064@FBGA48 [CX5002]  
EN29PL064@TSOP48 [CX1004]  
EN29SL160B@TSOP48 [CX1004]  
EN29SL160B@WPGA48 [CX5038]  
EN29SL160T@TSOP48 [CX1004]  
EN29SL160T@WPGA48 [CX5038]  
EN29SL400B@TSOP48 [CX1004]  
EN29SL400T@TSOP48 [CX1004]  
EN29SL800B@TSOP48 [CX1004]  
EN29SL800B@WPGA48 [CX5038]  
EN29SL800T@TSOP48 [CX1004]  
EN29SL800T@WPGA48 [CX5038]  
EN71PL032A0@FBGA56 [CX5045]  
EN71PL064B0@FBGA56 [CX5045]  
EN71SN10F@BGA130 [CX5140-1]

## EOREX

### E (E) PROM/FRAM/NVRAM

EM24LC02@SOP8 [CX1045]

## EPSON

### E (E) PROM/FRAM/NVRAM

S1H0H324B2B1@FBGA66 [CX5026]  
S1H0H326B2B1@FBGA66 [CX5026]  
S1H0H328B2B2@FBGA66 [CX5026]  
S1H0J642B2B3@FBGA68 [CX5026]  
S1H0J646B2B3@FBGA68 [CX5026]  
S1H0J648B2B2@FBGA68 [CX5026]

S1H0H324B2T1@FBGA66 [CX5026]  
S1H0H326B2T1@FBGA66 [CX5026]  
S1H0H328B2T2@FBGA66 [CX5026]  
S1H0J642B2T3@FBGA68 [CX5026]  
S1H0J646B2T3@FBGA68 [CX5026]  
S1H0J648B2T2@FBGA68 [CX5026]

## ESMT

### E (E) PROM/FRAM/NVRAM

EM25LV010@SOIC8 [CX1045]  
EM25LV512@SOIC8 [CX1045]  
F25D04QA@SOIC8 [CX1045#1]  
F25D08QA@SOIC8(150mil) [CX1045#1]  
F25D08QA@SOIC8(200mil) [CX1044#1]  
F25D08QA@WSON8 [CX4005#1]  
F25D64QA@WSON8 [CX4005]

EM25LV010@VFQFPN8 [CX4006]  
EM25LV512@VFQFPN8 [CX4006]  
F25D04QA@WSON8 [CX4005#1]  
F25D64QA@SOIC8 [CX1044#1]  
F25L004AB [CX0001]

F25L004AB@SOIC8(150mil) [CX1045]      F25L004AB@SOIC8(200mil) [CX1044]  
F25L004AT [CX0001]      F25L004AT@SOIC8(150mil) [CX1045]  
F25L004AT@SOIC8(200mil) [CX1044]      F25L008AB@SOIC8 [CX1044]  
F25L008AT@SOIC8 [CX1044]      F25L016AB@SOIC8 [CX1044]  
F25L016AT@SOIC8 [CX1044]      F25L01PA [CX0001]  
F25L01PA(2D)@SOIC8 [CX1045#1]      F25L01PA(2D)@TSSOP8 [CX1059#3]  
F25L01PA@SOIC8(150mil) [CX1045#1]  
F25L01PA@SOIC8(200mil) [CX1044#1]  
F25L02PA [CX0001]  
F25L02PA(2F)@SOIC8(150mil) [CX1045#1]  
F25L02PA(2F)@SOIC8(200mil) [CX1044#1]  
F25L02PA(2F)@WSON8 [CX4005#1]  
F25L02PA@SOIC8(150mil) [CX1045#1]  
F25L02PA@SOIC8(200mil) [CX1044#1]  
F25L04PA [CX0001]  
F25L04PA@SOIC8(150mil) [CX1045#1]  
F25L04PA@SOIC8(200mil) [CX1044#1]  
F25L05PA(2D)@SOIC8 [CX1045#1]      F25L05PA(2D)@TSSOP8 [CX1059#3]  
F25L08PA(2G) [CX0001]  
F25L08PA(2G)@SOIC8(150mil) [CX1045]  
F25L08PA(2G)@SOIC8(200mil) [CX1044]  
F25L08PA(2G)@WSON8 [CX4005]  
F25L08PA(AAI-PROGRAM)@SOIC8 [CX1044]  
F25L08PA(PAGE-PROGRAM)@SOIC8 [CX1044]  
F25L08QA(2S)@SOIC8(150mil) [CX1045#1]  
F25L08QA(2S)@SOIC8(200mil) [CX1044#1]  
F25L08QA@SOIC8(150mil) [CX1045#1]  
F25L08QA@SOIC8(200mil) [CX1044#1]  
F25L16PA(2S) [CX0001]      F25L16PA(2S)@SOIC16 [CX1033#1]  
F25L16PA(2S)@SOIC8(150mil) [CX1045#1]  
F25L16PA(2S)@SOIC8(200mil) [CX1044#1]  
F25L16PA(2S)@WSON8 [CX4005]  
F25L16PA(AAI-PROGRAM)@SOIC8 [CX1044]  
F25L16PA(PAGE-PROGRAM)@SOIC8 [CX1044]  
F25L16QA [CX0001]      F25L16QA@SOIC16 [CX1033#1]  
F25L16QA@SOIC8(150mil) [CX1045]      F25L16QA@SOIC8(200mil) [CX1044]  
F25L16QA@WSON8 [CX4005]  
F25L320PA(4K OTP)@SOIC16 [CX1033#1]  
F25L320PA(4K OTP)@SOIC8 [CX1044#1]  
F25L320PA@SOIC16 [CX1033#1]      F25L320PA@SOIC8 [CX1044#1]  
F25L32PA(4K OTP)(new)@SOIC16 [CX1033#1]  
F25L32PA(4K OTP)(new)@SOIC8 [CX1044#1]  
F25L32PA(4K OTP)@SOIC16 [CX1033#1]  
F25L32PA(4K OTP)@SOIC8 [CX1044#1]  
F25L32PA(new)@SOIC16 [CX1033#1]      F25L32PA(new)@SOIC8 [CX1044#1]  
F25L32PA@SOIC16 [CX1033#1]      F25L32PA@SOIC8 [CX1044#1]  
F25L32QA(2S)@SOIC16 [CX1033#1]      F25L32QA(2S)@SOIC8 [CX1044#1]  
F25L32QA(2S)@WSON8 [CX4005]  
F25L32QA(4K OTP)@SOIC16 [CX1033#1]  
F25L32QA(4K OTP)@SOIC8 [CX1044#1]  
F25L32QA@SOIC16 [CX1033#1]      F25L32QA@SOIC8 [CX1044#1]  
F25L64QA@BGA24 [CX5146]      F25L64QA@SOIC16 [CX1033#1]  
F25L64QA@SOIC8 [CX1044#1]      F25L64QA@WSON8 [CX4005]  
F29L064BGA@TSOP48 [CX1004]      F29L064UGA@TSOP48 [CX1004]  
F49B002UA [CX0001]      F49B002UA@PLCC32 [CX2032]  
F49L004BA@PLCC32 [CX2032]      F49L004BA@TSOP40 [CX1006]  
F49L004UA@PLCC32 [CX2032]      F49L004UA@TSOP40 [CX1006]  
F49L040A@PLCC32 [CX2032]      F49L040A@VSOP32 [CX1003]  
F49L160BA@TSOP48 [CX1004]      F49L160UA@TSOP48 [CX1004]

F49L320BA@TSOP48 [CX1004]  
F49L400BA@TSOP48 [CX1004]  
F49L800BA@TSOP48 [CX1004]  
F59L1G81A@BGA63 [CX5046-1]  
F59L2G81A@BGA63 [CX5046-1]  
F59L4G81A@TSOP48 [CX1004-3]  
FM91D06432UNA@FBGA56 [CX5045]  
FM91L01604UA@FBGA56 [CX5045]  
FM91L03204UA@FBGA56 [CX5045]  
FM91L03208BIA@FBGA56 [CX5045]  
FM91L03208UIA@FBGA56 [CX5045]  
FM91L03216UA@FBGA56 [CX5045]

F49L320UA@TSOP48 [CX1004]  
F49L400UA@TSOP48 [CX1004]  
F49L800UA@TSOP48 [CX1004]  
F59L1G81A@TSOP48 [CX1004-3]  
F59L2G81A@TSOP48 [CX1004-3]  
FM91D06432BNA@FBGA56 [CX5045]  
FM91L01604BA@FBGA56 [CX5045]  
FM91L03204BA@FBGA56 [CX5045]  
FM91L03208BA@FBGA56 [CX5045]  
FM91L03208UA@FBGA56 [CX5045]  
FM91L03216BA@FBGA56 [CX5045]

## ESTEK

### E (E) PROM/FRAM/NVRAM

24C02 [CX0001]  
24C02@TSSOP8 [CX1059]  
24C04@SOP8 [CX1045]  
24C08 [CX0001]  
24C08@TSSOP8 [CX1059]  
24C16@SOP8 [CX1045]  
K24C32 [CX0001]  
K24C32@TSSOP8 [CX1059]  
K24C64@SOP8 [CX1045]

24C02@SOP8 [CX1045]  
24C04 [CX0001]  
24C04@TSSOP8 [CX1059]  
24C08@SOP8 [CX1045]  
24C16 [CX0001]  
24C16@TSSOP8 [CX1059]  
K24C32@SOP8 [CX1045]  
K24C64 [CX0001]  
K24C64@TSSOP8 [CX1059]

## E-TRAND

### E (E) PROM/FRAM/NVRAM

AMI29DL163BT@TSOP48 [CX1004]

AMI29DL163TT@TSOP48 [CX1004]

## EVERSPIN

### E (E) PROM/FRAM/NVRAM

M24A16B@FBGA48 [CX5085]  
MR0A08B@FBGA48 [CX5085]  
MR0A08B@TSOP44 [CX1046]  
MR0A16A@TSOP44 [CX1046]  
MR0A16B@TSOP44 [CX1046]  
MR256A08@FBGA48 [CX5085]  
MR256A08@TSOP44 [CX1046]  
MR256A08B@SOIC32 [CX1069]  
MR256D08B@FBGA48 [CX5085]  
MR25H10CDCR [CX4005#1]  
MR25H10MDCR [CX4005#1]  
MR25H256CDCR [CX4005#1]  
MR25H256MDCR [CX4005#1]  
MR25H40CDCR [CX4005#1]  
MR25H40MDC [CX4005#1]  
MR25H40MPU [CX0001]  
MR2A08A@TSOP44 [CX1046]  
MR2A16A@TSOP44 [CX1046]  
MR4A08B@TSOP44 [CX1046]

M24A16B@TSOP44 [CX1046]  
MR0A08B@SOIC32 [CX1069]  
MR0A16A@FBGA48 [CX5085]  
MR0A16B@FBGA48 [CX5085]  
MR0D08B@FBGA48 [CX5085]  
MR256A08@SOIC32 [CX1069]  
MR256A08B@FBGA48 [CX5085]  
MR256A08B@TSOP44 [CX1046]  
MR25H10CDC [CX4005#1]  
MR25H10MDC [CX4005#1]  
MR25H256CDC [CX4005#1]  
MR25H256MDC [CX4005#1]  
MR25H40CDC [CX4005#1]  
MR25H40CPU [CX0001]  
MR25H40MDCR [CX4005#1]  
MR2A08A@FBGA48 [CX5085]  
MR2A16A@FBGA48 [CX5085]  
MR4A08B@FBGA48 [CX5085]  
MR4A16B@FBGA48 [CX5085]

MR4A16B@TSOP48 [CX1007]

MR4A16B@TSOP54 [CX1010]

## EVERSTAR

### E (E) PROM/FRAM/NVRAM

EV29LV160AB [CX0001]  
EV29LV640MB [CX0001]

EV29LV160AT [CX0001]  
EV29LV640MT [CX0001]

## EXCELSEMI

### E (E) PROM/FRAM/NVRAM

ES25M16 [CX0001]  
ES25M16@SOP8[150 mil] [CX1044#1]  
ES25M40 [CX0001]  
ES25M40@SOP8[150 mil] [CX1044#1]  
ES25M80 [CX0001]  
ES25M80@SOP8[150 mil] [CX1044#1]  
ES25P16@SOP8 [CX1044#1]  
ES25P80@SOP8 [CX1044#1]  
ES29LV160DB@PSOP44 [CX1014]  
ES29LV160DT@FBGA48 [CX5002]  
ES29LV160DT@TSOP48 [CX1004]  
ES29LV160EB@TSOP48 [CX1004]  
ES29LV160ET@TSOP48 [CX1004]  
ES29LV160FB@TSOP48 [CX1004]  
ES29LV160FT@TSOP48 [CX1004]  
ES29LV320DB@TSOP48 [CX1004]  
ES29LV320DT@TSOP48 [CX1004]  
ES29LV320EB@TSOP48 [CX1004]  
ES29LV320ET@TSOP48 [CX1004]  
ES29LV320FB@TSOP48 [CX1004]  
ES29LV320FT@TSOP48 [CX1004]  
ES29LV400DB@TSOP48 [CX1004]  
ES29LV400DT@TSOP48 [CX1004]  
ES29LV400EB@TSOP48 [CX1004]  
ES29LV400ET@TSOP48 [CX1004]  
ES29LV800DB@PSOP44 [CX1014]  
ES29LV800DT@FBGA48 [CX5002]  
ES29LV800DT@TSOP48 [CX1004]  
ES29LV800EB@TSOP48 [CX1004]  
ES29LV800ET@TSOP48 [CX1004]

ES25M16@SOP16 [CX1033#1]  
ES25M16@SOP8[208 mil] [CX1045#1]  
ES25M40@SOP16 [CX1033#1]  
ES25M40@SOP8[208 mil] [CX1045#1]  
ES25M80@SOP16 [CX1033#1]  
ES25M80@SOP8[208 mil] [CX1045#1]  
ES25P40@SOP8 [CX1044#1]  
ES29LV160DB@FBGA48 [CX5002]  
ES29LV160DB@TSOP48 [CX1004]  
ES29LV160DT@PSOP44 [CX1014]  
ES29LV160EB@FBGA48 [CX5002]  
ES29LV160ET@FBGA48 [CX5002]  
ES29LV160FB@FBGA48 [CX5002]  
ES29LV160FT@FBGA48 [CX5002]  
ES29LV320DB@FBGA48 [CX5022]  
ES29LV320DT@FBGA48 [CX5022]  
ES29LV320EB@FBGA48 [CX5002]  
ES29LV320ET@FBGA48 [CX5002]  
ES29LV320FB@FBGA48 [CX5002]  
ES29LV320FT@FBGA48 [CX5002]  
ES29LV400DB@FBGA48 [CX5002]  
ES29LV400DT@FBGA48 [CX5002]  
ES29LV400EB@FBGA48 [CX5002]  
ES29LV400ET@FBGA48 [CX5002]  
ES29LV800DB@FBGA48 [CX5002]  
ES29LV800DB@TSOP48 [CX1004]  
ES29LV800DT@PSOP44 [CX1014]  
ES29LV800EB@FBGA48 [CX5002]  
ES29LV800ET@FBGA48 [CX5002]

## EXEL

### E (E) PROM/FRAM/NVRAM

XL24C01A [CX0001]  
XL24C04 [CX0001]  
XL24C16@SOIC8 [CX1045]  
XL28C256 [CX0001]  
XL28C256@TSOP28 [CX1024]  
XL9010(F) [CX1045]  
XL9020(F) [CX1045]  
XL9040(F) [CX1045]

XL24C02 [CX0001]  
XL24C16 [CX0001]  
XL24C32 [CX0001]  
XL28C256@PLCC32 [CX2032]  
XL9010 [CX0001]  
XL9020 [CX0001]  
XL9040 [CX0001]  
XL9346 [CX0001]

XL9346@SOIC8 [CX1045]	XL93CS56 [CX0001]
XL93CS56@SOIC8 [CX1045]	XL93CS56@TSSOP8 [CX1059]
XL93CS66 [CX0001]	XL93CS66@SOIC8 [CX1045]
XL93CS66@TSSOP8 [CX1059]	XL93LC46 [CX0001]
XL93LC46@SOIC8 [CX1045]	XL93LC46A [CX0001]
XL93LC46A@SOIC8 [CX1045]	XL93LC56 [CX0001]
XL93LC56@SOIC8 [CX1045]	XL93LC56A [CX0001]
XL93LC56A@SOIC8 [CX1045]	XL93LC66A [CX0001]
XL93LC66A@SOIC8 [CX1045]	XL9764 [CX0001]
XLE28C16A [CX0001]	XLE28C16A@PLCC32 [CX2032]
XLE28C16B [CX0001]	XLE28C16B@PLCC32 [CX2032]
XLE28C16B@SOIC24 [CX1033]	XLM28C16A [CX0001]
XLM28C16A@PLCC32 [CX2032]	XLM46C15 [CX0001]
XLM46P15 [CX0001]	XLS2804A [CX0001]
XLS2816A [CX0001]	XLS2816A@PLCC32 [CX2032]
XLS2817A [CX0001]	XLS28C16A [CX0001]
XLS28C16A@PLCC32 [CX2032]	XLS28C16B [CX0001]
XLS28C16B@PLCC32 [CX2032]	XLS28C16B@SOIC24 [CX1033]
XLS28C64B [CX0001]	XLS28C64B@PLCC32 [CX2032]
XLS28C64B@SOIC28 [CX1033]	XLS46C15 [CX0001]
XLS46P15 [CX0001]	XLS93C46 [CX0001]
XLS93C46@SOIC8 [CX1045]	XLS93C56 [CX0001]
XLS93C56@SOIC8 [CX1045]	XLS93C66 [CX0001]
XLS93C66@SOIC8 [CX1045]	XLS93CS46 [CX0001]
XLS93CS46@SOIC8 [CX1045]	XLS93CS46@TSSOP8 [CX1059]
XLS93LC06 [CX0001]	XLS93LC06@SOIC8 [CX1045]
XLS93LC66 [CX0001]	XLS93LC66@SOIC8 [CX1045]

## FAIRCHILD

### E (E) PROM/FRAM/NVRAM

FM24C02(M8)@SOIC8 [CX1045]	FM24C02(MT8)@TSSOP8 [CX1059]
FM24C02(N) [CX0001]	FM24C03(M8)@SOIC8 [CX1045]
FM24C03(MT8)@TSSOP8 [CX1059]	FM24C03(N) [CX0001]
FM24C04(M8)@SOIC8 [CX1045]	FM24C04(MT8)@TSSOP8 [CX1059]
FM24C04(N) [CX0001]	FM24C05(M8)@SOIC8 [CX1045]
FM24C05(MT8)@TSSOP8 [CX1059]	FM24C05(N) [CX0001]
FM24C08(M8)@SOIC8 [CX1045]	FM24C08(MT8)@TSSOP8 [CX1059]
FM24C08(N) [CX0001]	FM24C09(M8)@SOIC8 [CX1045]
FM24C09(MT8)@TSSOP8 [CX1059]	FM24C09(N) [CX0001]
FM24C128(MT8)@TSSOP8 [CX1059]	FM24C128(MW8)@SOIC8 [CX1045]
FM24C128(N) [CX0001]	FM24C16(M8)@SOIC8 [CX1045]
FM24C16(MT8)@TSSOP8 [CX1059]	FM24C16(N) [CX0001]
FM24C17(M8)@SOIC8 [CX1045]	FM24C17(MT8)@TSSOP8 [CX1059]
FM24C17(N) [CX0001]	FM24C256(M8)@SOIC8 [CX1045]
FM24C256(N) [CX0001]	FM24C32(M8)@SOIC8 [CX1045]
FM24C32(N) [CX0001]	FM27C010 [CX0001]
FM27C010@PLCC32 [CX2032]	FM27C010@TSOP32 [CX1002]
FM27C040 [CX0001]	FM27C040@PLCC32 [CX2032]
FM27C040@TSOP32 [CX1002]	FM27C256 [CX0001]
FM27C256@PLCC32 [CX2032]	FM27C256Q [CX0001]
FM27C256Q@PLCC32 [CX2032]	FM27C512 [CX0001]
FM27C512@PLCC32 [CX2032]	
FM93C06(M8)(08bit)@SOIC8 [CX1045]	
FM93C06(M8)(16bit)@SOIC8 [CX1045]	
FM93C06(MT8)(08bit)@TSSOP8 [CX1059]	
FM93C06(MT8)(16bit)@TSSOP8 [CX1059]	

FM93C06(N)(08bit) [CX0001]	FM93C06(N)(16bit) [CX0001]
FM93C14(16bit) [CX0001]	FM93C46(M8)@SOIC8 [CX1045]
FM93C46(MT8)@TSSOP8 [CX1059]	FM93C46(N) [CX0001]
FM93C46A(M8)(08bit)@SOIC8 [CX1045]	
FM93C46A(M8)(16bit)@SOIC8 [CX1045]	
FM93C46A(MT8)(08bit)@TSSOP8 [CX1059]	
FM93C46A(MT8)(16bit)@TSSOP8 [CX1059]	
FM93C46A(N)(08bit) [CX0001]	FM93C46A(N)(16bit) [CX0001]
FM93C56(M8)@SOIC8 [CX1045]	FM93C56(MT8)@TSSOP8 [CX1059]
FM93C56(N) [CX0001]	
FM93C56A(M8)(08bit)@SOIC8 [CX1045]	
FM93C56A(M8)(16bit)@SOIC8 [CX1045]	
FM93C56A(MT8)(08bit)@TSSOP8 [CX1059]	
FM93C56A(MT8)(16bit)@TSSOP8 [CX1059]	
FM93C56A(N)(08bit) [CX0001]	FM93C56A(N)(16bit) [CX0001]
FM93C66(M8)@SOIC8 [CX1045]	FM93C66(MT8)@TSSOP8 [CX1059]
FM93C66(N) [CX0001]	
FM93C66A(M8)(08bit)@SOIC8 [CX1045]	
FM93C66A(M8)(16bit)@SOIC8 [CX1045]	
FM93C66A(MT8)(08bit)@TSSOP8 [CX1059]	
FM93C66A(MT8)(16bit)@TSSOP8 [CX1059]	
FM93C66A(N)(08bit) [CX0001]	FM93C66A(N)(16bit) [CX0001]
FM93C76(M8)(16bit)@SOIC8 [CX1045]	
FM93C76(MT8)(16bit)@TSSOP8 [CX1059]	
FM93C76(N)(16bit) [CX0001]	
FM93C76A(M8)(08bit)@SOIC8 [CX1045]	
FM93C76A(M8)(16bit)@SOIC8 [CX1045]	
FM93C76A(MT8)(08bit)@TSSOP8 [CX1059]	
FM93C76A(MT8)(16bit)@TSSOP8 [CX1059]	
FM93C76A(N)(08bit) [CX0001]	FM93C76A(N)(16bit) [CX0001]
FM93C86(M8)(16bit)@SOIC8 [CX1045]	
FM93C86(MT8)(16bit)@TSSOP8 [CX1059]	
FM93C86(N)(16bit) [CX0001]	
FM93C86A(M8)(08bit)@SOIC8 [CX1045]	
FM93C86A(M8)(16bit)@SOIC8 [CX1045]	
FM93C86A(MT8)(08bit)@TSSOP8 [CX1059]	
FM93C86A(MT8)(16bit)@TSSOP8 [CX1059]	
FM93C86A(N)(08bit) [CX0001]	FM93C86A(N)(16bit) [CX0001]
FM93CS06(M8)@SOIC8 [CX1045]	FM93CS06(MT8)@TSSOP8 [CX1059]
FM93CS06(N) [CX0001]	FM93CS46(M8)@SOIC8 [CX1045]
FM93CS46(MT8)@TSSOP8 [CX1059]	FM93CS46(N) [CX0001]
FM93CS56(M8)@SOIC8 [CX1045]	FM93CS56(MT8)@TSSOP8 [CX1059]
FM93CS56(N) [CX0001]	FM93CS66(M8)@SOIC8 [CX1045]
FM93CS66(MT8)@TSSOP8 [CX1059]	FM93CS66(N) [CX0001]
FM93S46(M8)@SOIC8 [CX1045]	FM93S46(MT8)@TSSOP8 [CX1059]
FM93S46(N) [CX0001]	FM93S56(M8)@SOIC8 [CX1045]
FM93S56(MT8)@TSSOP8 [CX1059]	FM93S56(N) [CX0001]
FM93S66(M8)@SOIC8 [CX1045]	FM93S66(MT8)@TSSOP8 [CX1059]
FM93S66(N) [CX0001]	MM2716 [CX0001]
MM2716E [CX0001]	NM24C02(M8)@SOIC8 [CX1045]
NM24C02(MT8)@TSSOP8 [CX1059]	NM24C02(N) [CX0001]
NM24C02L(M8)@SOIC8 [CX1045]	NM24C02L(MT8)@TSSOP8 [CX1059]
NM24C02L(N) [CX0001]	NM24C03(M8)@SOIC8 [CX1045]
NM24C03(MT8)@TSSOP8 [CX1059]	NM24C03(N) [CX0001]
NM24C04(M8)@SOIC8 [CX1045]	NM24C04(MT8)@TSSOP8 [CX1059]
NM24C04(N) [CX0001]	NM24C05(M8)@SOIC8 [CX1045]
NM24C05(MT8)@TSSOP8 [CX1059]	NM24C05(N) [CX0001]
NM24C08(M8)@SOIC8 [CX1045]	NM24C08(MT8)@TSSOP8 [CX1059]
NM24C08(N) [CX0001]	NM24C09(M8)@SOIC8 [CX1045]

NM24C09(MT8)@TSSOP8 [CX1059]  
NM24C16(M8)@SOIC8 [CX1045]  
NM24C16(N) [CX0001]  
NM24C17(MT8)@TSSOP8 [CX1059]  
NM24C65(M8)SOIC8 [CX1045]  
NM27C010 [CX0001]  
NM27C010@TSOP32 [CX1002]  
NM27C020@PLCC32 [CX2032]  
NM27C020Q [CX0001]  
NM27C020Q@TSOP32 [CX1002]  
NM27C040@PLCC32 [CX2032]  
NM27C128 [CX0001]  
NM27C210 [CX0001]  
NM27C240 [CX0001]  
NM27C256 [CX0001]  
NM27C512 [CX0001]  
NM27C64Q [CX0001]  
NM27LC256 [CX0001]  
NM27LC512 [CX0001]  
NM27LV010 [CX0001]  
NM27LV010@TSOP32 [CX1002]  
NM27LV210@PLCC44 [CX2044]  
NM27LV512@PLCC32 [CX2032]  
NM27P040@PLCC32 [CX2032]  
NM27P210 [CX0001]  
NM27P512 [CX0001]  
NM93C66(M8)(16bit)@SOIC8 [CX1045]  
NM93C66(MT8)(16bit)@TSSOP8 [CX1059]  
NM93C66(N)(16bit) [CX0001]  
NM93CS06(MT8)@TSSOP8 [CX1059]  
NM93CS46(M8)@SOIC8 [CX1045]  
NM93CS46(N) [CX0001]  
NM93CS56(MT8)@TSSOP8 [CX1059]  
NM93CS66(M8)@SOIC8 [CX1045]  
NM93CS66(N) [CX0001]  
NMC27C010 [CX0001]  
NMC27C010@TSOP32 [CX1002]  
NMC27C1024@PLCC44 [CX2044]  
NMC27C128B@PLCC32 [CX2032]  
NMC27C128BN@PLCC32 [CX2032]  
NMC27C128BQ@PLCC32 [CX2032]  
NMC27C16 [CX0001]  
NMC27C16BQE [CX0001]  
NMC27C16HQ [CX0001]  
NMC27C256 [CX0001]  
NMC27C256B [CX0001]  
NMC27C256Q [CX0001]  
NMC27C32 [CX0001]  
NMC27C32BQ [CX0001]  
NMC27C32EH [CX0001]  
NMC27C512 [CX0001]  
NMC27C512A [CX0001]  
NMC27C512AN [CX0001]  
NMC27C64 [CX0001]  
NMC27C64(N) [CX0001]  
NMC87C257Q [CX0001]  
NMC87C257V [CX0001]  
NMC9346(M8)(16bit)@SOIC8 [CX1045]  
NMC9346(MT8)(16bit)@TSSOP8 [CX1059]  
NM24C09(N) [CX0001]  
NM24C16(MT8)@TSSOP8 [CX1059]  
NM24C17(M8)@SOIC8 [CX1045]  
NM24C17(N) [CX0001]  
NM24C65(N) [CX0001]  
NM27C010@PLCC32 [CX2032]  
NM27C020 [CX0001]  
NM27C020@TSOP32 [CX1002]  
NM27C020Q@PLCC32 [CX2032]  
NM27C040 [CX0001]  
NM27C040@TSOP32 [CX1002]  
NM27C128@PLCC32 [CX2032]  
NM27C210@PLCC44 [CX2044]  
NM27C240@PLCC44 [CX2044]  
NM27C256@PLCC32 [CX2032]  
NM27C512@PLCC32 [CX2032]  
NM27C64Q@PLCC32 [CX2032]  
NM27LC256@PLCC32 [CX2032]  
NM27LC512@PLCC32 [CX2032]  
NM27LV010@PLCC32 [CX2032]  
NM27LV210 [CX0001]  
NM27LV512 [CX0001]  
NM27P040 [CX0001]  
NM27P040@TSOP32 [CX1002]  
NM27P210@PLCC44 [CX2044]  
NM27P512@PLCC32 [CX2032]  
NM93CS06(M8)@SOIC8 [CX1045]  
NM93CS06(N) [CX0001]  
NM93CS46(MT8)@TSSOP8 [CX1059]  
NM93CS56(M8)@SOIC8 [CX1045]  
NM93CS56(N) [CX0001]  
NM93CS66(MT8)@TSSOP8 [CX1059]  
NMC2732 [CX0001]  
NMC27C010@PLCC32 [CX2032]  
NMC27C1024 [CX0001]  
NMC27C128B [CX0001]  
NMC27C128BN [CX0001]  
NMC27C128BQ [CX0001]  
NMC27C128CQ [CX0001]  
NMC27C16BQ [CX0001]  
NMC27C16H [CX0001]  
NMC27C16Q [CX0001]  
NMC27C256@PLCC32 [CX2032]  
NMC27C256B@PLCC32 [CX2032]  
NMC27C256Q@PLCC32 [CX2032]  
NMC27C32B [CX0001]  
NMC27C32E [CX0001]  
NMC27C32H [CX0001]  
NMC27C512@PLCC32 [CX2032]  
NMC27C512A@PLCC32 [CX2032]  
NMC27C512AN@PLCC32 [CX2032]  
NMC27C64(BN) [CX0001]  
NMC27CP128 [CX0001]  
NMC87C257Q@PLCC32 [CX2032]  
NMC87C257V@PLCC32 [CX2032]



NMC9346(N)(16bit) [CX0001]  
 NMC93C46(M8)(16bit)@SOIC8 [CX1045]  
 NMC93C46(MT8)(16bit)@TSSOP8 [CX1059]  
 NMC93C46(N)(16bit) [CX0001]  
 NMC93C46A(M8)(16bit)@SOIC8 [CX1045]  
 NMC93C46A(MT8)(16bit)@TSSOP8 [CX1059]  
 NMC93C46A(N)(16bit) [CX0001]  
 NMC93C56(M8)(16bit)@SOIC8 [CX1045]  
 NMC93C56(MT8)(16bit)@TSSOP8 [CX1059]  
 NMC93C56(N)(16bit) [CX0001]  
 NMC93C66(M8)(16bit)@SOIC8 [CX1045]  
 NMC93C66(MT8)(16bit)@TSSOP8 [CX1059]  
 NMC93C66(N)(16bit) [CX0001]  
 NMC93CS06(MT8)@TSSOP8 [CX1059]  
 NMC93CS06(N) [CX0001]  
 NMC93CS46(M8)@SOIC8 [CX1045]  
 NMC93CS46(N) [CX0001]  
 NMC93CS46(MT8)@TSSOP8 [CX1059]  
 NMC93CS46(N) [CX0001]  
 NMC93CS56(M8)@SOIC8 [CX1045]  
 NMC93CS56(N) [CX0001]  
 NMC93CS66(M8)@SOIC8 [CX1045]  
 NMC93CS66(N) [CX0001]  
 NMC93CS66(MT8)@TSSOP8 [CX1059]  
 NMC93CS66(N) [CX0001]  
 NMC93CS06(M8)@SOIC8 [CX1045]  
 NMC93CS46(MT8)@TSSOP8 [CX1059]  
 NMC93CS56(M8)@SOIC8 [CX1045]  
 NMC93CS56(N) [CX0001]  
 NMC93CS66(MT8)@TSSOP8 [CX1059]  
 NMC9817 [CX0001]

## MICROCONTROLLER

ACE1001(M8)@SOIC8 [CX1045]  
 ACE1001(MT8)@TSSOP8 [CX1000]  
 ACE1001E(M8)@SOIC8 [CX1045]  
 ACE1001E(MT8)@TSSOP8 [CX1000]  
 ACE1001L(M8)@SOIC8 [CX1045]  
 ACE1001L(MT8)@TSSOP8 [CX1000]  
 ACE1101(EMT8)@TSSOP8 [CX1000]  
 ACE1101(EN) [CX0001]  
 ACE1101(LMT8)@TSSOP8 [CX1000]  
 ACE1101(LN) [CX0001]  
 ACE1101(MT8)@TSSOP8 [CX1000]  
 ACE1101(N) [CX0001]  
 ACE1101(VMT8)@TSSOP8 [CX1000]  
 ACE1101(VN) [CX0001]  
 ACE1101B(EMT8)@TSSOP8 [CX1000]  
 ACE1101B(EN) [CX0001]  
 ACE1101B(MT8)@TSSOP8 [CX1000]  
 ACE1101B(N) [CX0001]  
 ACE1101B(VMT8)@TSSOP8 [CX1000]  
 ACE1101B(VN) [CX0001]  
 ACE1202(dip14) [CX0001]  
 ACE1202(M14)@SOIC14 [CX1016]  
 ACE12022(dip14) [CX0001]  
 ACE12022(M14)@SOIC14 [CX1016]  
 ACE12022B(dip14) [CX0001]  
 ACE12022B(M14)@SOIC14 [CX1016]  
 ACE12022BE(dip14) [CX0001]  
 ACE12022BE(M14)@SOIC14 [CX1016]  
 ACE12022BV(dip14) [CX0001]  
 ACE12022BV(M14)@SOIC14 [CX1016]  
 ACE12022E(dip14) [CX0001]  
 ACE12022E(M14)@SOIC14 [CX1016]  
 ACE1202B(dip14) [CX0001]  
 ACE1202B(M14)@SOIC14 [CX1016]  
 ACE1202BE(dip14) [CX0001]  
 ACE1202BE(M14)@SOIC14 [CX1016]  
 ACE1202BV(dip14) [CX0001]  
 ACE1001(M8X)@SOIC8 [CX1045]  
 ACE1001(MT8X)@TSSOP8 [CX1000]  
 ACE1001E(M8X)@SOIC8 [CX1045]  
 ACE1001E(MT8X)@TSSOP8 [CX1000]  
 ACE1001L(M8X)@SOIC8 [CX1045]  
 ACE1001L(MT8X)@TSSOP8 [CX1000]  
 ACE1101(EMT8X)@TSSOP8 [CX1000]  
 ACE1101(EN14) [CX0001]  
 ACE1101(LMT8X)@TSSOP8 [CX1000]  
 ACE1101(LN14) [CX0001]  
 ACE1101(MT8X)@TSSOP8 [CX1000]  
 ACE1101(N14) [CX0001]  
 ACE1101(VMT8X)@TSSOP8 [CX1000]  
 ACE1101(VN14) [CX0001]  
 ACE1101B(EMT8X)@TSSOP8 [CX1000]  
 ACE1101B(EN14) [CX0001]  
 ACE1101B(MT8X)@TSSOP8 [CX1000]  
 ACE1101B(N14) [CX0001]  
 ACE1101B(VMT8X)@TSSOP8 [CX1000]  
 ACE1101B(VN14) [CX0001]  
 ACE1202(dip8) [CX0001]  
 ACE1202(M8)@SOIC8 [CX1045]  
 ACE12022(dip8) [CX0001]  
 ACE12022(M8)@SOIC8 [CX1045]  
 ACE12022B(dip8) [CX0001]  
 ACE12022B(M8)@SOIC8 [CX1045]  
 ACE12022BE(dip8) [CX0001]  
 ACE12022BE(M8)@SOIC8 [CX1045]  
 ACE12022BV(dip8) [CX0001]  
 ACE12022BV(M8)@SOIC8 [CX1045]  
 ACE12022E(dip8) [CX0001]  
 ACE12022E(M8)@SOIC8 [CX1045]  
 ACE1202B(dip8) [CX0001]  
 ACE1202B(M8)@SOIC8 [CX1045]  
 ACE1202BE(dip8) [CX0001]  
 ACE1202BE(M8)@SOIC8 [CX1045]  
 ACE1202BV(dip8) [CX0001]

ACE1202BV(M14)@SOIC14 [CX1016]	ACE1202BV(M8)@SOIC8 [CX1045]
ACE1202E(dip14) [CX0001]	ACE1202E(dip8) [CX0001]
ACE1202E(M14)@SOIC14 [CX1016]	ACE1202E(M8)@SOIC8 [CX1045]
ACE1202L(dip14) [CX0001]	ACE1202L(dip8) [CX0001]
ACE1202L(M14)@SOIC14 [CX1016]	ACE1202L(M8)@SOIC8 [CX1045]
ACE1202V(dip8)	ACE1202V(M14)@SOIC14 [CX1016]
ACE1202V(M8)@SOIC8 [CX1045]	ACE1501(EM)@SOIC14 [CX1016]
ACE1501(EM8)@SOIC8 [CX1045]	ACE1501(EM8X)@SOIC8 [CX1045]
ACE1501(EMT)@TSOP14 [CX1000]	ACE1501(EMT8)@TSSOP8 [CX1000]
ACE1501(EMT8X)@TSSOP8 [CX1000]	ACE1501(EMTX)@TSOP14 [CX1000]
ACE1501(EMX)@SOIC14 [CX1016]	ACE1501(EN) [CX0001]
ACE1501(EN14) [CX0001]	ACE1501(VM)@SOIC14 [CX1016]
ACE1501(VM8)@SOIC8 [CX1045]	ACE1501(VM8X)@SOIC8 [CX1045]
ACE1501(VMT)@TSOP14 [CX1000]	ACE1501(VMT8)@TSSOP8 [CX1000]
ACE1501(VMT8X)@TSSOP8 [CX1000]	ACE1501(VMTX)@TSOP14 [CX1000]
ACE1501(VMX)@SOIC14 [CX1016]	ACE1501(VN) [CX0001]
ACE1501(VN14) [CX0001]	ACE1502(EM)@SOIC14 [CX1016]
ACE1502(EM8)@SOIC8 [CX1045]	ACE1502(EMT)@TSOP14 [CX1000]
ACE1502(EMT8)@TSSOP8 [CX1000]	ACE1502(EN) [CX0001]
ACE1502(EN14) [CX0001]	ACE1502(VM)@SOIC14 [CX1016]
ACE1502(VM8)@SOIC8 [CX1045]	ACE1502(VMT)@TSOP14 [CX1000]
ACE1502(VMT8)@TSSOP8 [CX1000]	ACE1502(VN) [CX0001]
ACE1502(VN14) [CX0001]	ACE8000(M8)@SOIC8 [CX1045]
ACE8000(M8X)@SOIC8 [CX1045]	ACE8000E(M8)@SOIC8 [CX1045]
ACE8000E(M8X)@SOIC8 [CX1045]	ACE8001(M8)@SOIC8 [CX1045]
ACE8001(M8X)@SOIC8 [CX1045]	ACE8001(MT8)@TSSOP8 [CX1000]
ACE8001(MT8X)@TSSOP8 [CX1000]	ACE8001E(M8)@SOIC8 [CX1045]
ACE8001E(M8X)@SOIC8 [CX1045]	ACE8001E(MT8)@TSSOP8 [CX1000]
ACE8001E(MT8X)@TSSOP8 [CX1000]	FMS7401L(EM8X)@SOIC8 [CX1045]
FMS7401L(EMT8X)@TSSOP8 [CX1000]	FMS7401L(EMTX)@TSSOP14 [CX1000]
FMS7401L(EMX)@SOIC14 [CX1045]	FMS7401L(EN) [CX0001]
FMS7401L(EN14) [CX0001]	FMS7401L(VN) [CX0001]
FMS7401L(VN14) [CX0001]	

## FDI

### E (E) PROM/FRAM/NVRAM

MSP55LV100G(low)@FBGA96 [CX5028]	
MSP55LV100G(normal)@FBGA96 [CX5028]	
MSP55LV100G@FBGA96 [CX5028]	MSP55LV100GS@FBGA96 [CX5005]
MSP55LV128(fast)@PSOP44 [CX1014]	MSP55LV128@PSOP44 [CX1014]
MSP55LV128T(*8)@TSOP56 [CX1011]	
MSP55LV128T(fast)@PSOP44 [CX1014]	MSP55LV128T@TSOP56 [CX1011]
MSP55LV128T@PSOP44 [CX1014]	MSP55LV160A@PSOP44 [CX1014]
MSP55LV160@PSOP44 [CX1014]	MSP55LV256@PSOP44 [CX1014]
MSP55LV256(fast)@PSOP44 [CX1014]	
MSP55LV512@SSOP70 [CX1057]	MSP55LV512@SSOP70(new) [CX1057]
MSP55LV650@PSOP44 [CX1014]	

## FIDELIX

### E (E) PROM/FRAM/NVRAM

FM25M04A [CX0001#1]  
 FM25M04A@SOIC8(150 mil) [CX1045#1]  
 FM25M04A@SOIC8(200 mil) [CX1044#1]

FM25M04A@USON8 [CX4002#1]	FM25M04A@VSOP8 [CX1044#1]
FM25M04A@WSON8 [CX4005#1]	FM25M08A [CX0001#1]
FM25M08A@SOIC16 [CX1033#1]	
FM25M08A@SOIC8(150 mil) [CX1045#1]	
FM25M08A@SOIC8(200 mil) [CX1044#1]	
FM25M08A@TFBGA24 [CX5146]	FM25M08A@VSOP8 [CX1044#1]
FM25M08A@WSON8 [CX4005#1]	FM25M16A [CX0001#1]
FM25M16A@SOIC16 [CX1033#1]	
FM25M16A@SOIC8(150 mil) [CX1045#1]	
FM25M16A@SOIC8(200 mil) [CX1044#1]	
FM25M16A@TFBGA24 [CX5146]	FM25M16A@VSOP8 [CX1059#3]
FM25M16A@WSON8 [CX4005#1]	FM25M32A [CX0001#1]
FM25M32A@SOIC16 [CX1033#1]	
FM25M32A@SOIC8(150 mil) [CX1045#1]	
FM25M32A@SOIC8(200 mil) [CX1044#1]	
FM25M32A@TFBGA24 [CX5146]	FM25M32A@VSOP8 [CX1045#1]
FM25M32A@WSON8 [CX4005#1]	FM25M64A [CX0001#1]
FM25M64A@SOIC16 [CX1033#1]	
FM25M64A@SOIC8(150 mil) [CX1045#1]	
FM25M64A@SOIC8(200 mil) [CX1044#1]	
FM25M64A@TFBGA24 [CX5146]	FM25M64A@VSOP8 [CX1045#1]
FM25M64A@WSON8 [CX4005#1]	
FM25Q08@SOIC8(150 mil) [CX1045#1]	
FM25Q08A [CX0001#1]	FM25Q08A@SOIC16 [CX1033#1]
FM25Q08A@SOIC8(200 mil) [CX1044#1]	
FM25Q08A@TFBGA24 [CX5146]	FM25Q08A@VSOP8 [CX1059#3]
FM25Q08A@WSON8 [CX4005#1]	FM25Q16 [CX0001#1]
FM25Q16@SOP8 [CX1044#1]	FM25Q16@WSON8 [CX4005#1]
FM25Q16A [CX0001#1]	FM25Q16A@SOP8 [CX1045#1]
FM25Q16A@WSON8 [CX4005#1]	FM25Q16A-B24 [CX5146]
FM25Q16A-S16 [CX1033#1]	FM25Q16A-T08 [CX1044#1]
FM25Q16A-V08 [CX1059#3]	FM25Q16B [CX0001#1]
FM25Q16B-B24 [CX5146]	FM25Q16B-S08 [CX1045#1]
FM25Q16B-S16 [CX1033#1]	FM25Q16B-T08 [CX1044#1]
FM25Q16B-V08 [CX1059#3]	FM25Q16B-W08 [CX4005#1]
FM25Q32A [CX0001#1]	FM25Q32A@SOP16 [CX1033#1]
FM25Q32A@SOP8(150 mil) [CX1045#1]	
FM25Q32A@SOP8(200 mil) [CX1044#1]	
FM25Q32A@WSON8 [CX4005#1]	FM25Q32A-B24 [CX5146]
FM25Q32A-V08 [CX1045#1]	FM25Q64A [CX0001#1]
FM25Q64A-B24 [CX5146]	FM25Q64A-S08 [CX1045#1]
FM25Q64A-S16 [CX1033#1]	FM25Q64A-T08 [CX1044#1]
FM25Q64A-V08 [CX1045#1]	FM25Q64A-W08 [CX4005#1]
FM25S16A [CX0001#1]	FM25S16A-B24 [CX5146]
FM25S16A-S08 [CX1045#1]	FM25S16A-S16 [CX1033#1]
FM25S16A-T08 [CX1044#1]	FM25S16A-V08 [CX1059#3]
FM25S16A-W08 [CX4005#1]	

## FIRST-RANK Technology

### E (E) PROM/FRAM/NVRAM

T24C02 [CX0001]	T24C02@SOP8 [CX1045]
T24C02@TSSOP8 [CX1059]	T24C04 [CX0001]
T24C04@SOP8 [CX1045]	T24C04@TSSOP8 [CX1059]
T24C08 [CX0001]	T24C08@SOP8 [CX1045]
T24C08@TSSOP8 [CX1059]	T24C16 [CX0001]
T24C16@SOP8 [CX1045]	T24C16@TSSOP8 [CX1059]

# FLEXTRONICS

## MICROCONTROLLER

LPC2368@BGA100(new) [CX5055]

# FORCE TECHNOLOGIES

## E (E) PROM/FRAM/NVRAM

FT24C01 [CX0001]  
FT24C01@TSOP8 [CX1059]  
FT24C01A@SOIC8 [CX1045]  
FT24C02 [CX0001]  
FT24C02@TSOP8 [CX1059]  
FT24C02A@SOIC8 [CX1045]  
FT24C04 [CX0001]  
FT24C04@TSOP8 [CX1059]  
FT24C04A@SOIC8 [CX1045]  
FT24C08 [CX0001]  
FT24C08@TSOP8 [CX1059]  
FT24C08A@SOIC8 [CX1045]  
FT24C128 [CX0001]  
FT24C128@TSOP8 [CX1059]  
FT24C128A@SOIC8 [CX1045]  
FT24C16 [CX0001]  
FT24C16@TSOP8 [CX1059]  
FT24C16A@SOIC8 [CX1045]  
FT24C256 [CX0001]  
FT24C256@TSOP8 [CX1059]  
FT24C256A@SOIC8 [CX1045]  
FT24C32 [CX0001]  
FT24C32@TSOP8 [CX1059]  
FT24C32A@SOIC8 [CX1045]  
FT24C64 [CX0001]  
FT24C64@TSOP8 [CX1059]  
FT24C64A@SOIC8 [CX1045]  
FT27C010 [CX0001]  
FT27C010@TSOP32 [CX1002]  
FT27C020@PLCC32 [CX2032]  
FT27C040 [CX0001]  
FT27C040@TSOP32 [CX1002]  
FT27C256 [CX0001]  
FT27C64 [CX0001]  
FT27HC256 [CX0001]  
FT27HC64 [CX0001]  
FT28C010 [CX0001]  
FT28C010@PLCC32 [CX2032]  
FT28C010@TSOP32 [CX1002]  
FT28C010E@JLCC32 [CX2132]  
FT28C010E@PLCC44 [CX2044]  
FT28C020 [CX0001]  
FT28C020@PLCC32 [CX2032]  
FT28C020@TSOP32 [CX1002]  
FT28C040@JLCC32 [CX2132]  
FT28C040@PLCC44 [CX2044]  
FT24C01@SOIC8 [CX1045]  
FT24C01A [CX0001]  
FT24C01A@TSOP8 [CX1059]  
FT24C02@SOIC8 [CX1045]  
FT24C02A [CX0001]  
FT24C02A@TSOP8 [CX1059]  
FT24C04@SOIC8 [CX1045]  
FT24C04A [CX0001]  
FT24C04A@TSOP8 [CX1059]  
FT24C08@SOIC8 [CX1045]  
FT24C08A [CX0001]  
FT24C08A@TSOP8 [CX1059]  
FT24C128@SOIC8 [CX1045]  
FT24C128A [CX0001]  
FT24C128A@TSOP8 [CX1059]  
FT24C16@SOIC8 [CX1045]  
FT24C16A [CX0001]  
FT24C16A@TSOP8 [CX1059]  
FT24C256@SOIC8 [CX1045]  
FT24C256A [CX0001]  
FT24C256A@TSOP8 [CX1059]  
FT24C32@SOIC8 [CX1045]  
FT24C32A [CX0001]  
FT24C32A@TSOP8 [CX1059]  
FT24C64@SOIC8 [CX1045]  
FT24C64A [CX0001]  
FT24C64A@TSOP8 [CX1059]  
FT27C010@PLCC32 [CX2032]  
FT27C020 [CX0001]  
FT27C020@TSOP32  
FT27C040@PLCC32 [CX2032]  
FT27C16 [CX0001]  
FT27C256@PLCC32 [CX2032]  
FT27C64@PLCC32 [CX2032]  
FT27HC256@PLCC32 [CX2032]  
FT27HC64@PLCC32 [CX2032]  
FT28C010@JLCC32 [CX2132]  
FT28C010@PLCC44 [CX2044]  
FT28C010E [CX0001]  
FT28C010E@PLCC32 [CX2032]  
FT28C010E@TSOP32 [CX1002]  
FT28C020@JLCC32 [CX2132]  
FT28C020@PLCC44 [CX2044]  
FT28C040 [CX0001]  
FT28C040@PLCC32 [CX2032]  
FT28C040@TSOP32 [CX1002]

FT28C16 [CX0001]  
FT28C256 [CX0001]  
FT28C256@PLCC32 [CX2032]  
FT28C256@TSOP28 [CX1024]  
FT28C256B@JLCC32 [CX2132]  
FT28C256B@SOIC28 [CX1033]  
FT28C64 [CX0001]  
FT28C64@SOIC28 [CX1033]  
FT28C64B [CX0001]  
FT28C64B@PLCC32 [CX2032]  
FT28C64B@TSOP28 [CX1024]  
FT28C64X@PLCC32 [CX2032]  
FT28C64X@TSOP28 [CX1024]  
FT28HC64@PLCC32 [CX2032]  
FT58C1001 [CX0001]  
FT58C1001@VSOP32 [CX1003]

FT28C16@PLCC32 [CX2032]  
FT28C256@JLCC32 [CX2132]  
FT28C256@SOIC28 [CX1033]  
FT28C256B [CX0001]  
FT28C256B@PLCC32 [CX2032]  
FT28C256B@TSOP28 [CX1024]  
FT28C64@PLCC32 [CX2032]  
FT28C64@TSOP28 [CX1024]  
FT28C64B@JLCC32 [CX2132]  
FT28C64B@SOIC28 [CX1033]  
FT28C64X [CX0001]  
FT28C64X@SOIC28 [CX1033]  
FT28HC64 [CX0001]  
FT28HC64@TSOP28 [CX1024]  
FT58C1001@SSOP32 [CX1020]

## FORCREAT

### MICROCONTROLLER

uPD78F0524AGB@QFP52 [CX3010]

uPD78F0524GB@QFP52 [CX3010]

## FORWARD

### E (E) PROM/FRAM/NVRAM

24LC01 [CX0001]  
24LC02 [CX0001]  
24LC04 [CX0001]  
24LC08 [CX0001]  
24LC16 [CX0001]  
24LC32 [CX0001]  
24LC64 [CX0001]

24LC01@SOIC8 [CX1045]  
24LC02@SOIC8 [CX1045]  
24LC04@SOIC8 [CX1045]  
24LC08@SOIC8 [CX1045]  
24LC16@SOIC8 [CX1045]  
24LC32@SOIC8 [CX1045]  
24LC64@SOIC8 [CX1045]

## FREESCALE

### E (E) PROM/FRAM/NVRAM

MR2A16A@TSOP44 [CX1046]

### MICROCONTROLLER

DSP56F801(FA60)@TQFP48 [CX3007]  
DSP56F801(FA80)@TQFP48 [CX3007]  
DSP56F802(TA60)@TQFP32 [CX3001]  
DSP56F802(TA80)@TQFP32 [CX3001]  
MC56F8002VWL@SOIC28 [CX1033]  
MC56F8006VLF@QFP48 [CX3007]  
MC56F8011VFAE@QFP32 [CX3001]  
MC56F8014VFAE@QFP32 [CX3001]  
MC56F8023VFAE@QFP32 [CX3001]  
MC56F8027VLD@QFP64 [CX3011]  
MC56F8035VLD@QFP44 [CX3003]  
MC56F8036VFAE@QFP48 [CX3007]

DSP56F801(FA60E)@TQFP48 [CX3007]  
DSP56F801(FA80E)@TQFP48 [CX3007]  
DSP56F802(TA60E)@TQFP32 [CX3001]  
DSP56F802(TA80E)@TQFP32 [CX3001]  
MC56F8006VLC@QFP32 [CX3001]  
MC56F8006VWL@SOIC28 [CX1033]  
MC56F8013VFAE@QFP32 [CX3001]  
MC56F8023MFAE@QFP32 [CX3001]  
MC56F8025VLD@QFP44 [CX3003]  
MC56F8033VLC@QFP32 [CX3001]  
MC56F8036MFAE@QFP48 [CX3007]  
MC56F8037VLH@QFP64 [CX3011]

MC56F8122MFA@QFP48 [CX3007]  
MC56F8122VFA@QFP48 [CX3007]  
MC56F8123MFB@QFP64 [CX3011]  
MC56F8123VFB@QFP64 [CX3011]  
MC56F8246MLF@QFP48 [CX3007]  
MC56F8247MLH@QFP64 [CX3011]  
MC56F8256MLF@QFP48 [CX3007]  
MC56F8257MLH@QFP64 [CX3011]  
MC56F8322MFA@QFP48 [CX3007]  
MC56F8322VFA@QFP48 [CX3007]  
MC56F8323MFB@QFP64 [CX3011]  
MC56F8323VFB@QFP64 [CX3011]  
MC68HC11E1@PLCC52 [CX2052]  
MC68HC11E1CFN2 [CX2052]  
MC68HC11E1CFU2 [CX3044]  
MC68HC11E1MFN2 [CX2052]  
MC68HC11E1VFN2 [CX2052]  
MC68HC11E20@PLCC52 [CX2052]  
MC68HC11E20CFN2 [CX2052]  
MC68HC11E20CFU2 [CX3044]  
MC68HC11E20MFN2 [CX2052]  
MC68HC11E20VFN2 [CX2052]  
MC68HC11E9@PLCC52 [CX2052]  
MC68HC11E9CFN2 [CX2052]  
MC68HC11E9CFU2 [CX3044]  
MC68HC11E9MFN2 [CX2052]  
MC68HC11E9VFN2 [CX2052]  
MC68HC11EA9CFN2 [CX2052]  
MC68HC11EA9CFS2 [CX2052]  
MC68HC11EA9MFN2 [CX2052]  
MC68HC11EA9MFS2 [CX2052]  
MC68HC11EA9VFN2 [CX2052]  
MC68HC11EA9VFS2 [CX2052]  
MC68HC11F1@PLCC68 [CX2068]  
MC68HC11F1ACFN2 [CX2068]  
MC68HC11F1ACFN4 [CX2068]  
MC68HC11F1ACPU3 [CX3017]  
MC68HC11F1AMFN2 [CX2068]  
MC68HC11F1AMFN4 [CX2068]  
MC68HC11F1AMPU3 [CX3017]  
MC68HC11F1AVFN2 [CX2068]  
MC68HC11F1AVFN4 [CX2068]  
MC68HC11F1AVPU3 [CX3017]  
MC68HC11F1CFN2 [CX2068]  
MC68HC11F1CFN4 [CX2068]  
MC68HC11F1CPU3 [CX3017]  
MC68HC11F1MFN2 [CX2068]  
MC68HC11F1MFN4 [CX2068]  
MC68HC11F1MPU3 [CX3017]  
MC68HC11F1VFN2 [CX2068]  
MC68HC11F1VFN4 [CX2068]  
MC68HC11F1VPU3 [CX3017]  
MC68HC11K1@PLCC84 [CX2084]  
MC68HC11KS2@PLCC68 [CX2068]  
MC68HC705B16CB [CX0056]  
MC68HC705B16CFU [CX3013]  
MC68HC705B16FU [CX3013]  
MC68HC705B16NCB [CX0056]  
MC68HC705B16NCFU [CX3013]

MC56F8122MFAE@QFP48 [CX3007]  
MC56F8122VFAE@QFP48 [CX3007]  
MC56F8123MFBE@QFP64 [CX3011]  
MC56F8123VFBE@QFP64 [CX3011]  
MC56F8246VLF@QFP48 [CX3007]  
MC56F8247VLH@QFP64 [CX3011]  
MC56F8256VLF@QFP48 [CX3007]  
MC56F8257VLH@QFP64 [CX3011]  
MC56F8322MFAE@QFP48 [CX3007]  
MC56F8322VFAE@QFP48 [CX3007]  
MC56F8323MFBE@QFP64 [CX3011]  
MC56F8323VFBE@QFP64 [CX3011]  
MC68HC11E1@QFP52 [CX3010]  
MC68HC11E1CFN3 [CX2052]  
MC68HC11E1CFU3 [CX3044]  
MC68HC11E1MFU2 [CX3044]  
MC68HC11E1VFU2 [CX3044]  
MC68HC11E20@QFP52 [CX3010]  
MC68HC11E20CFN3 [CX2052]  
MC68HC11E20CFU3 [CX3044]  
MC68HC11E20MFU2 [CX3044]  
MC68HC11E20VFU2 [CX3044]  
MC68HC11E9@QFP52 [CX3010]  
MC68HC11E9CFN3 [CX2052]  
MC68HC11E9CFU3 [CX3044]  
MC68HC11E9MFU2 [CX3044]  
MC68HC11E9VFU2 [CX3044]  
MC68HC11EA9CFN3 [CX2052]  
MC68HC11EA9CFS3 [CX2052]  
MC68HC11EA9MFN3 [CX2052]  
MC68HC11EA9MFS3 [CX2052]  
MC68HC11EA9VFN3 [CX2052]  
MC68HC11EA9VFS3 [CX2052]  
MC68HC11F1A@PLCC68 [CX2068]  
MC68HC11F1ACFN3 [CX2068]  
MC68HC11F1ACPU2 [CX3017]  
MC68HC11F1ACPU4 [CX3017]  
MC68HC11F1AMFN3 [CX2068]  
MC68HC11F1AMPU2 [CX3017]  
MC68HC11F1AMPU4 [CX3017]  
MC68HC11F1AVFN3 [CX2068]  
MC68HC11F1AVPU2 [CX3017]  
MC68HC11F1AVPU4 [CX3017]  
MC68HC11F1CFN3 [CX2068]  
MC68HC11F1CPU2 [CX3017]  
MC68HC11F1CPU4 [CX3017]  
MC68HC11F1MFN3 [CX2068]  
MC68HC11F1MPU2 [CX3017]  
MC68HC11F1MPU4 [CX3017]  
MC68HC11F1VFN3 [CX2068]  
MC68HC11F1VPU2 [CX3017]  
MC68HC11F1VPU4 [CX3017]  
MC68HC11K1@TQFP80 [CX3018]  
MC68HC705B16B [CX0056]  
MC68HC705B16CFN [CX2052]  
MC68HC705B16FN [CX2052]  
MC68HC705B16NB [CX0056]  
MC68HC705B16NCFN [CX2052]  
MC68HC705B16NFN [CX2052]

MC68HC705B16NFU [CX3013]  
MC68HC705C4@PLCC44 [CX2044]  
MC68HC705C4A@PLCC44 [CX2044]  
MC68HC705C8@PLCC44 [CX2044]  
MC68HC705C8@TQFP44 [CX3002]  
MC68HC705C8A@PLCC44 [CX2044]  
MC68HC705C8A@TQFP44 [CX3002]  
MC68HC705C9A@PLCC44 [CX2044]  
MC68HC705P6(CDW)@SOIC28 [CX1033]  
MC68HC705P6A(CDW)@SOIC28 [CX1033]  
MC68HC705P6A(CP) [CX0001]  
MC68HC705P9@SOIC28 [CX1033]  
MC68HC711E9@PLCC52 [CX2052]  
MC68HC711E9CFN2@PLCC52 [CX2052]  
MC68HC711E9CFNE@PLCC52 [CX2052]  
MC68HC711E9CFNE3@PLCC52 [CX2052]  
MC68HC711E9MFN2@PLCC52 [CX2052]  
MC68HC711E9VFN2@PLCC52 [CX2052]  
MC68HC711EA9CFN2 [CX2052]  
MC68HC711EA9CFS2 [CX2052]  
MC68HC711EA9MFN2 [CX2052]  
MC68HC711EA9MFS2 [CX2052]  
MC68HC711EA9VFN2 [CX2052]  
MC68HC711EA9VFS2 [CX2052]  
MC68HC711K4@PLCC84 [CX2084]  
MC68HC711KA2@PLCC68 [CX2068]  
MC68HC711KA4@PLCC68 [CX2068]  
MC68HC711L6@PLCC68 [CX2068]  
MC68HC811E2 [CX0001]  
MC68HC811E2C [CX0001]  
MC68HC811E2V [CX0001]  
MC68HC908AB32CFUE@TQFP64 [CX3014]  
MC68HC908AB32MFU@TQFP64 [CX3014]  
MC68HC908AB32MFUE@TQFP64 [CX3014]  
MC68HC908AB32VFU@TQFP64 [CX3014]  
MC68HC908AB32VFUE@TQFP64 [CX3014]  
MC68HC908AP16CB@SDIP42 [CX0042]  
MC68HC908AP16CFA@LQFP48 [CX3007]  
MC68HC908AP16CFAE@LQFP48 [CX3007]  
MC68HC908AP16CFB@TQFP44 [CX3002]  
MC68HC908AP16CFBE@TQFP44 [CX3002]  
MC68HC908AP16MB@SDIP42 [CX0042]  
MC68HC908AP16MFA@LQFP48 [CX3007]  
MC68HC908AP16MFAE@LQFP48 [CX3007]  
MC68HC908AP16MFB@TQFP44 [CX3002]  
MC68HC908AP16MFBE@TQFP44 [CX3002]  
MC68HC908AP16VB@SDIP42 [CX0042]  
MC68HC908AP16VFA@LQFP48 [CX3007]  
MC68HC908AP16VFAE@LQFP48 [CX3007]  
MC68HC908AP16VFB@TQFP44 [CX3002]  
MC68HC908AP16VFBE@TQFP44 [CX3002]  
MC68HC908AP32CB@SDIP42 [CX0042]  
MC68HC908AP32CFA@LQFP48 [CX3007]  
MC68HC908AP32CFAE@LQFP48 [CX3007]  
MC68HC908AP32CFB@TQFP44 [CX3002]  
MC68HC908AP32CFBE@TQFP44 [CX3002]  
MC68HC908AP32MB@SDIP42 [CX0042]  
MC68HC908AP32MFA@LQFP48 [CX3007]  
MC68HC908AP32MFAE@LQFP48 [CX3007]

MC68HC705C4 [CX0001]  
MC68HC705C4A [CX0001]  
MC68HC705C8 [CX0001]  
MC68HC705C8@SDIP42 [CX0042]  
MC68HC705C8A [CX0001]  
MC68HC705C8A@SDIP42 [CX0042]  
MC68HC705C9A [CX0001]  
MC68HC705C9A@TQFP44 [CX3002]  
MC68HC705P6(CP) [CX0001]  
MC68HC705P9 [CX0001]  
MC68HC711E20@PLCC52 [CX2052]  
MC68HC711E9CFN@PLCC52 [CX2052]  
MC68HC711E9CFN3@PLCC52 [CX2052]  
MC68HC711E9CFNE2@PLCC52 [CX2052]  
MC68HC711E9FN@PLCC52 [CX2052]  
MC68HC711E9MFNE2@PLCC52 [CX2052]  
MC68HC711E9VFNE2@PLCC52 [CX2052]  
MC68HC711EA9CFN3 [CX2052]  
MC68HC711EA9CFS3 [CX2052]  
MC68HC711EA9MFN3 [CX2052]  
MC68HC711EA9MFS3 [CX2052]  
MC68HC711EA9VFN3 [CX2052]  
MC68HC711EA9VFS3 [CX2052]  
MC68HC711K4@TQFP80 [CX3018]  
MC68HC711KA3@PLCC68 [CX2068]  
MC68HC711KS2@PLCC68 [CX2068]  
MC68HC711L6@TQFP64 [CX3013]  
MC68HC811E2@PLCC52 [CX2052]  
MC68HC811E2M [CX0001]  
MC68HC908AB32CFU@TQFP64 [CX3014]  
MC68HC908AP16CBE@SDIP42 [CX0042]  
MC68HC908AP16MBE@SDIP42 [CX0042]  
MC68HC908AP16VBE@SDIP42 [CX0042]  
MC68HC908AP32CBE@SDIP42 [CX0042]  
MC68HC908AP32MBE@SDIP42 [CX0042]

MC68HC908AP32MFB@TQFP44 [CX3002]  
MC68HC908AP32MFB@TQFP44 [CX3002]  
MC68HC908AP32VB@SDIP42 [CX0042] MC68HC908AP32VBE@SDIP42 [CX0042]  
MC68HC908AP32VFA@LQFP48 [CX3007]  
MC68HC908AP32VFAE@LQFP48 [CX3007]  
MC68HC908AP32VFB@TQFP44 [CX3002]  
MC68HC908AP32VFBE@TQFP44 [CX3002]  
MC68HC908AP64CB@SDIP42 [CX0042] MC68HC908AP64CBE@SDIP42 [CX0042]  
MC68HC908AP64CFA@LQFP48 [CX3007]  
MC68HC908AP64CFAE@LQFP48 [CX3007]  
MC68HC908AP64CFB@TQFP44 [CX3002]  
MC68HC908AP64CFBE@TQFP44 [CX3002]  
MC68HC908AP64MB@SDIP42 [CX0042] MC68HC908AP64MBE@SDIP42 [CX0042]  
MC68HC908AP64MFA@LQFP48 [CX3007]  
MC68HC908AP64MFAE@LQFP48 [CX3007]  
MC68HC908AP64MFB@TQFP44 [CX3002]  
MC68HC908AP64MFB@TQFP44 [CX3002]  
MC68HC908AP64VB@SDIP42 [CX0042] MC68HC908AP64VBE@SDIP42 [CX0042]  
MC68HC908AP64VFA@LQFP48 [CX3007]  
MC68HC908AP64VFAE@LQFP48 [CX3007]  
MC68HC908AP64VFB@TQFP44 [CX3002]  
MC68HC908AP64VFBE@TQFP44 [CX3002]  
MC68HC908AP8CB@SDIP42 [CX0042] MC68HC908AP8CBE@SDIP42 [CX0042]  
MC68HC908AP8CFA@LQFP48 [CX3007] MC68HC908AP8CFAE@LQFP48 [CX3007]  
MC68HC908AP8CFB@TQFP44 [CX3002] MC68HC908AP8CFBE@TQFP44 [CX3002]  
MC68HC908AP8MB@SDIP42 [CX0042] MC68HC908AP8MBE@SDIP42 [CX0042]  
MC68HC908AP8MFA@LQFP48 [CX3007] MC68HC908AP8MFAE@LQFP48 [CX3007]  
MC68HC908AP8MFB@TQFP44 [CX3002] MC68HC908AP8MFB@TQFP44 [CX3002]  
MC68HC908AP8VB@SDIP42 [CX0042] MC68HC908AP8VBE@SDIP42 [CX0042]  
MC68HC908AP8VFA@LQFP48 [CX3007] MC68HC908AP8VFAE@LQFP48 [CX3007]  
MC68HC908AP8VFB@TQFP44 [CX3002] MC68HC908AP8VFBE@TQFP44 [CX3002]  
MC68HC908AS32ACFN@PLCC52 [CX2052]  
MC68HC908AS32ACFNE@PLCC52 [CX2052]  
MC68HC908AS32ACFU@TQFP64 [CX3014]  
MC68HC908AS32ACFUE@TQFP64 [CX3014]  
MC68HC908AS32AMFN@PLCC52 [CX2052]  
MC68HC908AS32AMFNE@PLCC52 [CX2052]  
MC68HC908AS32AMFU@TQFP64 [CX3014]  
MC68HC908AS32AMFUE@TQFP64 [CX3014]  
MC68HC908AS32AVFN@PLCC52 [CX2052]  
MC68HC908AS32AVFNE@PLCC52 [CX2052]  
MC68HC908AS32AVFU@TQFP64 [CX3014]  
MC68HC908AS32AVFUE@TQFP64 [CX3014]  
MC68HC908AS60ACFN@PLCC52 [CX2052]  
MC68HC908AS60ACFU@TQFP64 [CX3014]  
MC68HC908AS60AMFN@PLCC52 [CX2052]  
MC68HC908AS60AMFU@TQFP64 [CX3014]  
MC68HC908AS60AVFN@PLCC52 [CX2052]  
MC68HC908AS60AVFU@TQFP64 [CX3014]  
MC68HC908AS60CFN@PLCC52 [CX2052] MC68HC908AS60CFU@TQFP64 [CX3014]  
MC68HC908AS60MFN@PLCC52 [CX2052] MC68HC908AS60MFU@TQFP64 [CX3014]  
MC68HC908AS60VFN@PLCC52 [CX2052] MC68HC908AS60VFU@TQFP64 [CX3014]  
MC68HC908AZ32ACFU@TQFP64 [CX3014]  
MC68HC908AZ32ACFUE@TQFP64 [CX3014]  
MC68HC908AZ32AMFU@TQFP64 [CX3014]  
MC68HC908AZ32AMFUE@TQFP64 [CX3014]  
MC68HC908AZ32AVFU@TQFP64 [CX3014]  
MC68HC908AZ32AVFUE@TQFP64 [CX3014]  
MC68HC908AZ60ACFU@TQFP64 [CX3014]



MC68HC908AZ60ACFUE@TQFP64 [CX3014]  
MC68HC908AZ60AMFU@TQFP64 [CX3014]  
MC68HC908AZ60AMFUE@TQFP64 [CX3014]  
MC68HC908AZ60AVFU@TQFP64 [CX3014]  
MC68HC908AZ60AVFUE@TQFP64 [CX3014]  
MC68HC908AZ60CFU@TQFP64 [CX3014] MC68HC908AZ60MFU@TQFP64 [CX3014]  
MC68HC908AZ60VFU@TQFP64 [CX3014] MC68HC908BD48IB@SDIP42 [CX0042]  
MC68HC908BD48IB@SDIP42 [CX0042] MC68HC908BD48IFB@TQFP44 [CX3002]  
MC68HC908BD48IFBE@TQFP44 [CX3002]  
MC68HC908EY16ACFJ@TQFP32 [CX3001]  
MC68HC908EY16ACFJE@TQFP32 [CX3001]  
MC68HC908EY16AKFJ@TQFP32 [CX3001]  
MC68HC908EY16AKFJE@TQFP32 [CX3001]  
MC68HC908EY16AMFJ@TQFP32 [CX3001]  
MC68HC908EY16AMFJE@TQFP32 [CX3001]  
MC68HC908EY16AVFJ@TQFP32 [CX3001]  
MC68HC908EY16AVFJE@TQFP32 [CX3001]  
MC68HC908EY16CFA@TQFP32 [CX3001]  
MC68HC908EY16CFAE@TQFP32 [CX3001]  
MC68HC908EY16KFA@TQFP32 [CX3001]  
MC68HC908EY16KFAE@TQFP32 [CX3001]  
MC68HC908EY16MFA@TQFP32 [CX3001]  
MC68HC908EY16MFAE@TQFP32 [CX3001]  
MC68HC908EY16VFA@TQFP32 [CX3001]  
MC68HC908EY16VFAE@TQFP32 [CX3001]  
MC68HC908EY8ACFJ@TQFP32 [CX3001]  
MC68HC908EY8ACFJE@TQFP32 [CX3001]  
MC68HC908EY8AKFJ@TQFP32 [CX3001]  
MC68HC908EY8AKFJE@TQFP32 [CX3001]  
MC68HC908EY8AMFJ@TQFP32 [CX3001]  
MC68HC908EY8AMFJE@TQFP32 [CX3001]  
MC68HC908EY8AVFJ@TQFP32 [CX3001]  
MC68HC908EY8AVFJE@TQFP32 [CX3001]  
MC68HC908EY8CFA@TQFP32 [CX3001] MC68HC908EY8CFAE@TQFP32 [CX3001]  
MC68HC908EY8KFA@TQFP32 [CX3001] MC68HC908EY8KFAE@TQFP32 [CX3001]  
MC68HC908EY8MFA@TQFP32 [CX3001] MC68HC908EY8MFAE@TQFP32 [CX3001]  
MC68HC908EY8VFA@TQFP32 [CX3001] MC68HC908EY8VFAE@TQFP32 [CX3001]  
MC68HC908GP32CB@SDIP42 [CX0042] MC68HC908GP32CBE@SDIP42 [CX0042]  
MC68HC908GP32CFB@TQFP44 [CX3002]  
MC68HC908GP32CFBE@TQFP44 [CX3002]  
MC68HC908GP32CP MC68HC908GP32CPE  
MC68HC908GP32MB@SDIP42 [CX0042] MC68HC908GP32MBE@SDIP42 [CX0042]  
MC68HC908GP32MFB@TQFP44 [CX3002]  
MC68HC908GP32MFBE@TQFP44 [CX3002]  
MC68HC908GP32MP MC68HC908GP32MPE  
MC68HC908GP32VB@SDIP42 [CX0042] MC68HC908GP32VBE@SDIP42 [CX0042]  
MC68HC908GP32VFB@TQFP44 [CX3002]  
MC68HC908GP32VFBE@TQFP44 [CX3002]  
MC68HC908GP32VP MC68HC908GP32VPE  
MC68HC908GR16ACFA@TQFP48 [CX3007]  
MC68HC908GR16ACFAE@TQFP48 [CX3007]  
MC68HC908GR16ACFJ@TQFP32 [CX3001]  
MC68HC908GR16ACFJE@TQFP32 [CX3001]  
MC68HC908GR16AMFA@TQFP48 [CX3007]  
MC68HC908GR16AMFAE@TQFP48 [CX3007]  
MC68HC908GR16AMFJ@TQFP32 [CX3001]  
MC68HC908GR16AMFJE@TQFP32 [CX3001]  
MC68HC908GR16AVFA@TQFP48 [CX3007]  
MC68HC908GR16AVFAE@TQFP48 [CX3007]

MC68HC908GR16AVFJ@TQFP32 [CX3001]  
MC68HC908GR16AVFJE@TQFP32 [CX3001]  
MC68HC908GR16CFA@TQFP48 [CX3007]  
MC68HC908GR16CFAE@TQFP48 [CX3007]  
MC68HC908GR16CFJ@TQFP32 [CX3001]  
MC68HC908GR16CFJE@TQFP32 [CX3001]  
MC68HC908GR16MFA@TQFP48 [CX3007]  
MC68HC908GR16MFAE@TQFP48 [CX3007]  
MC68HC908GR16MFJ@TQFP32 [CX3001]  
MC68HC908GR16MFJE@TQFP32 [CX3001]  
MC68HC908GR16VFA@TQFP48 [CX3007]  
MC68HC908GR16VFAE@TQFP48 [CX3007]  
MC68HC908GR16VFJ@TQFP32 [CX3001]  
MC68HC908GR16VFJE@TQFP32 [CX3001]  
MC68HC908GR32ACFA@TQFP48 [CX3007]  
MC68HC908GR32ACFAE@TQFP48 [CX3007]  
MC68HC908GR32ACFJ@TQFP32 [CX3001]  
MC68HC908GR32ACFJE@TQFP32 [CX3001]  
MC68HC908GR32ACFU@QFP64 [CX3014]  
MC68HC908GR32ACFUE@QFP64 [CX3014]  
MC68HC908GR32AMFA@TQFP48 [CX3007]  
MC68HC908GR32AMFAE@TQFP48 [CX3007]  
MC68HC908GR32AMFJ@TQFP32 [CX3001]  
MC68HC908GR32AMFJE@TQFP32 [CX3001]  
MC68HC908GR32AMFU@QFP64 [CX3014]  
MC68HC908GR32AMFUE@QFP64 [CX3014]  
MC68HC908GR32AVFA@TQFP48 [CX3007]  
MC68HC908GR32AVFAE@TQFP48 [CX3007]  
MC68HC908GR32AVFJ@TQFP32 [CX3001]  
MC68HC908GR32AVFJE@TQFP32 [CX3001]  
MC68HC908GR32AVFU@QFP64 [CX3014]  
MC68HC908GR32AVFUE@QFP64 [CX3014]  
MC68HC908GR48ACFA@TQFP48 [CX3007]  
MC68HC908GR48ACFAE@TQFP48 [CX3007]  
MC68HC908GR48ACFJ@TQFP32 [CX3001]  
MC68HC908GR48ACFJE@TQFP32 [CX3001]  
MC68HC908GR48ACFU@QFP64 [CX3014]  
MC68HC908GR48ACFUE@QFP64 [CX3014]  
MC68HC908GR48AMFA@TQFP48 [CX3007]  
MC68HC908GR48AMFAE@TQFP48 [CX3007]  
MC68HC908GR48AMFJ@TQFP32 [CX3001]  
MC68HC908GR48AMFJE@TQFP32 [CX3001]  
MC68HC908GR48AMFU@QFP64 [CX3014]  
MC68HC908GR48AMFUE@QFP64 [CX3014]  
MC68HC908GR48AVFA@TQFP48 [CX3007]  
MC68HC908GR48AVFAE@TQFP48 [CX3007]  
MC68HC908GR48AVFJ@TQFP32 [CX3001]  
MC68HC908GR48AVFJE@TQFP32 [CX3001]  
MC68HC908GR48AVFU@QFP64 [CX3014]  
MC68HC908GR48AVFUE@QFP64 [CX3014]  
MC68HC908GR4ACDW@SOIC28 [CX1033]  
MC68HC908GR4ACDWE@SOIC28 [CX1033]  
MC68HC908GR4ACFA@TQFP32 [CX3001]  
MC68HC908GR4ACFAE@TQFP32 [CX3001]  
MC68HC908GR4ACP  
MC68HC908GR4AMDW@SOIC28 [CX1033]  
MC68HC908GR4AMDWE@SOIC28 [CX1033]  
MC68HC908GR4AMFA@TQFP32 [CX3001]  
MC68HC908GR4AMFAE@TQFP32 [CX3001]

MC68HC908GR4ACPE

MC68HC908GR4AMP  
MC68HC908GR4AVDW@SOIC28 [CX1033]  
MC68HC908GR4AVDWE@SOIC28 [CX1033]  
MC68HC908GR4AVFA@TQFP32 [CX3001]  
MC68HC908GR4AVFAE@TQFP32 [CX3001]  
MC68HC908GR4AVP  
MC68HC908GR4CB@SDIP42 [CX0042]  
MC68HC908GR4CDW@SOIC28 [CX1033]  
MC68HC908GR4CFA@TQFP32 [CX3001]  
MC68HC908GR4CP  
MC68HC908GR4MB@SDIP42 [CX0042]  
MC68HC908GR4MDW@SOIC28 [CX1033]  
MC68HC908GR4MFA@TQFP32 [CX3001]  
MC68HC908GR4MP  
MC68HC908GR4VB@SDIP42 [CX0042]  
MC68HC908GR4VDW@SOIC28 [CX1033]  
MC68HC908GR4VFA@TQFP32 [CX3001]  
MC68HC908GR4VP  
MC68HC908GR60ACFA@TQFP48 [CX3007]  
MC68HC908GR60ACFAE@TQFP48 [CX3007]  
MC68HC908GR60ACFJ@TQFP32 [CX3001]  
MC68HC908GR60ACFJE@TQFP32 [CX3001]  
MC68HC908GR60ACFU@QFP64 [CX3014]  
MC68HC908GR60ACFUE@QFP64 [CX3014]  
MC68HC908GR60AMFA@TQFP48 [CX3007]  
MC68HC908GR60AMFAE@TQFP48 [CX3007]  
MC68HC908GR60AMFJ@TQFP32 [CX3001]  
MC68HC908GR60AMFJE@TQFP32 [CX3001]  
MC68HC908GR60AMFU@QFP64 [CX3014]  
MC68HC908GR60AMFUE@QFP64 [CX3014]  
MC68HC908GR60AVFA@TQFP48 [CX3007]  
MC68HC908GR60AVFAE@TQFP48 [CX3007]  
MC68HC908GR60AVFJ@TQFP32 [CX3001]  
MC68HC908GR60AVFJE@TQFP32 [CX3001]  
MC68HC908GR60AVFU@QFP64 [CX3014]  
MC68HC908GR60AVFUE@QFP64 [CX3014]  
MC68HC908GR8ACDW@SOIC28 [CX1033]  
MC68HC908GR8ACDWE@SOIC28 [CX1033]  
MC68HC908GR8ACFA@TQFP32 [CX3001]  
MC68HC908GR8ACFAE@TQFP32 [CX3001]  
MC68HC908GR8ACP  
MC68HC908GR8AMDW@SOIC28 [CX1033]  
MC68HC908GR8AMDWE@SOIC28 [CX1033]  
MC68HC908GR8AMFA@TQFP32 [CX3001]  
MC68HC908GR8AMFAE@TQFP32 [CX3001]  
MC68HC908GR8AMP  
MC68HC908GR8AVDW@SOIC28 [CX1033]  
MC68HC908GR8AVDWE@SOIC28 [CX1033]  
MC68HC908GR8AVFA@TQFP32 [CX3001]  
MC68HC908GR8AVFAE@TQFP32 [CX3001]  
MC68HC908GR8AVP  
MC68HC908GR8CB@SDIP42 [CX0042]  
MC68HC908GR8CDW@SOIC28 [CX1033]  
MC68HC908GR8CFA@TQFP32 [CX3001]  
MC68HC908GR8CP  
MC68HC908GR8MB@SDIP42 [CX0042]  
MC68HC908GR8MDW@SOIC28 [CX1033]  
MC68HC908GR8MFA@TQFP32 [CX3001]  
MC68HC908GR8MP

MC68HC908GR4AMPE  
  
MC68HC908GR4AVPE  
MC68HC908GR4CBE@SDIP42 [CX0042]  
MC68HC908GR4CDWE@SOIC28 [CX1033]  
MC68HC908GR4CFAE@TQFP32 [CX3001]  
MC68HC908GR4CPE  
MC68HC908GR4MBE@SDIP42 [CX0042]  
MC68HC908GR4MDWE@SOIC28 [CX1033]  
MC68HC908GR4MFAE@TQFP32 [CX3001]  
MC68HC908GR4MPE  
MC68HC908GR4VBE@SDIP42 [CX0042]  
MC68HC908GR4VDWE@SOIC28 [CX1033]  
MC68HC908GR4VFAE@TQFP32 [CX3001]  
MC68HC908GR4VPE  
  
MC68HC908GR8ACP  
  
MC68HC908GR8AMPE  
  
MC68HC908GR8AVPE  
MC68HC908GR8CBE@SDIP42 [CX0042]  
MC68HC908GR8CDWE@SOIC28 [CX1033]  
MC68HC908GR8CFAE@TQFP32 [CX3001]  
MC68HC908GR8CPE  
MC68HC908GR8MBE@SDIP42 [CX0042]  
MC68HC908GR8MDWE@SOIC28 [CX1033]  
MC68HC908GR8MFAE@TQFP32 [CX3001]  
MC68HC908GR8MPE

MC68HC908GR8VB@SDIP42 [CX0042]      MC68HC908GR8VBE@SDIP42 [CX0042]  
MC68HC908GR8VDW@SOIC28 [CX1033]      MC68HC908GR8VDWE@SOIC28 [CX1033]  
MC68HC908GR8VFA@TQFP32 [CX3001]      MC68HC908GR8VFAE@TQFP32 [CX3001]  
MC68HC908GR8VP  
MC68HC908GT16CB@SDIP42 [CX0042]      MC68HC908GT16CBE@SDIP42 [CX0042]  
MC68HC908GT16CFB@TQFP44 [CX3002]      MC68HC908GT16MBE@SDIP42 [CX0042]  
MC68HC908GT16CFBE@TQFP44 [CX3002]      MC68HC908GT16VBE@SDIP42 [CX0042]  
MC68HC908GT16MB@SDIP42 [CX0042]      MC68HC908GT8CBE@SDIP42 [CX0042]  
MC68HC908GT16MFB@TQFP44 [CX3002]      MC68HC908GT8CFBE@TQFP44 [CX3002]  
MC68HC908GT16MFBE@TQFP44 [CX3002]      MC68HC908GT8MBE@SDIP42 [CX0042]  
MC68HC908GT16VB@SDIP42 [CX0042]      MC68HC908GT8MFBE@TQFP44 [CX3002]  
MC68HC908GT16VFB@TQFP44 [CX3002]      MC68HC908GT8VBE@SDIP42 [CX0042]  
MC68HC908GT16VFBE@TQFP44 [CX3002]      MC68HC908GT8VFBE@TQFP44 [CX3002]  
MC68HC908GT8CB@SDIP42 [CX0042]      MC68HC908GZ16CFA@TQFP48 [CX3007]  
MC68HC908GT8CFB@TQFP44 [CX3002]      MC68HC908GZ16CFAE@TQFP48 [CX3007]  
MC68HC908GT8MB@SDIP42 [CX0042]      MC68HC908GZ16CFJ@TQFP32 [CX3001]  
MC68HC908GT8MFB@TQFP44 [CX3002]      MC68HC908GZ16CFJE@TQFP32 [CX3001]  
MC68HC908GT8VB@SDIP42 [CX0042]      MC68HC908GZ16MFA@TQFP48 [CX3007]  
MC68HC908GT8VFB@TQFP44 [CX3002]      MC68HC908GZ16MFAE@TQFP48 [CX3007]  
MC68HC908GZ16CFA@TQFP48 [CX3007]      MC68HC908GZ16MFJ@TQFP32 [CX3001]  
MC68HC908GZ16CFAE@TQFP48 [CX3007]      MC68HC908GZ16MFJE@TQFP32 [CX3001]  
MC68HC908GZ16CFJ@TQFP32 [CX3001]      MC68HC908GZ16VFA@TQFP48 [CX3007]  
MC68HC908GZ16CFJE@TQFP32 [CX3001]      MC68HC908GZ16VFAE@TQFP48 [CX3007]  
MC68HC908GZ16MFA@TQFP48 [CX3007]      MC68HC908GZ16VFJ@TQFP32 [CX3001]  
MC68HC908GZ16MFAE@TQFP48 [CX3007]      MC68HC908GZ16VFJE@TQFP32 [CX3001]  
MC68HC908GZ16MFJ@TQFP32 [CX3001]      MC68HC908GZ32CFA@TQFP48 [CX3007]  
MC68HC908GZ16MFJE@TQFP32 [CX3001]      MC68HC908GZ32CFAE@TQFP48 [CX3007]  
MC68HC908GZ16VFA@TQFP48 [CX3007]      MC68HC908GZ32CFJ@TQFP32 [CX3001]  
MC68HC908GZ16VFAE@TQFP48 [CX3007]      MC68HC908GZ32CFJE@TQFP32 [CX3001]  
MC68HC908GZ16VFJ@TQFP32 [CX3001]      MC68HC908GZ32CFU@QFP64 [CX3014]  
MC68HC908GZ16VFJE@TQFP32 [CX3001]      MC68HC908GZ32MFA@TQFP48 [CX3007]  
MC68HC908GZ32CFA@TQFP48 [CX3007]      MC68HC908GZ32MFAE@TQFP48 [CX3007]  
MC68HC908GZ32CFAE@TQFP48 [CX3007]      MC68HC908GZ32MFJ@TQFP32 [CX3001]  
MC68HC908GZ32CFJ@TQFP32 [CX3001]      MC68HC908GZ32MFJE@TQFP32 [CX3001]  
MC68HC908GZ32CFJE@TQFP32 [CX3001]      MC68HC908GZ32MFU@QFP64 [CX3014]  
MC68HC908GZ32CFU@QFP64 [CX3014]      MC68HC908GZ32VFA@TQFP48 [CX3007]  
MC68HC908GZ32MFA@TQFP48 [CX3007]      MC68HC908GZ32VFAE@TQFP48 [CX3007]  
MC68HC908GZ32MFAE@TQFP48 [CX3007]      MC68HC908GZ32VFJ@TQFP32 [CX3001]  
MC68HC908GZ32MFJ@TQFP32 [CX3001]      MC68HC908GZ32VFJE@TQFP32 [CX3001]  
MC68HC908GZ32MFJE@TQFP32 [CX3001]      MC68HC908GZ32VFU@QFP64 [CX3014]  
MC68HC908GZ32MFU@QFP64 [CX3014]      MC68HC908GZ32VFUE@QFP64 [CX3014]  
MC68HC908GZ32VFA@TQFP48 [CX3007]      MC68HC908GZ48CFA@TQFP48 [CX3007]  
MC68HC908GZ32VFAE@TQFP48 [CX3007]      MC68HC908GZ48CFAE@TQFP48 [CX3007]  
MC68HC908GZ32VFJ@TQFP32 [CX3001]      MC68HC908GZ48CFJ@TQFP32 [CX3001]  
MC68HC908GZ32VFJE@TQFP32 [CX3001]      MC68HC908GZ48CFJE@TQFP32 [CX3001]  
MC68HC908GZ48CFA@TQFP48 [CX3007]      MC68HC908GZ48CFU@QFP64 [CX3014]  
MC68HC908GZ48CFAE@TQFP48 [CX3007]      MC68HC908GZ48CFUE@QFP64 [CX3014]  
MC68HC908GZ48CFJ@TQFP32 [CX3001]      MC68HC908GZ48MFA@TQFP48 [CX3007]  
MC68HC908GZ48CFJE@TQFP32 [CX3001]      MC68HC908GZ48MFAE@TQFP48 [CX3007]  
MC68HC908GZ48CFU@QFP64 [CX3014]      MC68HC908GZ48MFJ@TQFP32 [CX3001]  
MC68HC908GZ48MFA@TQFP48 [CX3007]      MC68HC908GZ48MFJE@TQFP32 [CX3001]  
MC68HC908GZ48MFAE@TQFP48 [CX3007]      MC68HC908GZ48MFU@QFP64 [CX3014]  
MC68HC908GZ48MFJ@TQFP32 [CX3001]      MC68HC908GZ48VFU@QFP64 [CX3014]  
MC68HC908GZ48MFJE@TQFP32 [CX3001]      MC68HC908GZ48VFA@TQFP48 [CX3007]  
MC68HC908GZ48MFU@QFP64 [CX3014]      MC68HC908GZ48VFAE@TQFP48 [CX3007]  
MC68HC908GZ48VFA@TQFP48 [CX3007]      MC68HC908GZ48VFJ@TQFP32 [CX3001]  
MC68HC908GZ48VFAE@TQFP48 [CX3007]

MC68HC908GZ48VFJE@TQFP32 [CX3001]  
MC68HC908GZ48VFU@QFP64 [CX3014]  
MC68HC908GZ60CFA@TQFP48 [CX3007]  
MC68HC908GZ60CFAE@TQFP48 [CX3007]  
MC68HC908GZ60CFJ@TQFP32 [CX3001]  
MC68HC908GZ60CFJE@TQFP32 [CX3001]  
MC68HC908GZ60CFU@QFP64 [CX3014]  
MC68HC908GZ60MFA@TQFP48 [CX3007]  
MC68HC908GZ60MFAE@TQFP48 [CX3007]  
MC68HC908GZ60MFJ@TQFP32 [CX3001]  
MC68HC908GZ60MFJE@TQFP32 [CX3001]  
MC68HC908GZ60MFU@QFP64 [CX3014]  
MC68HC908GZ60VFA@TQFP48 [CX3007]  
MC68HC908GZ60VFAE@TQFP48 [CX3007]  
MC68HC908GZ60VFJ@TQFP32 [CX3001]  
MC68HC908GZ60VFJE@TQFP32 [CX3001]  
MC68HC908GZ60VFU@QFP64 [CX3014]  
MC68HC908GZ8CFA@TQFP48 [CX3007]  
MC68HC908GZ8CFJ@TQFP32 [CX3001]  
MC68HC908GZ8MFA@TQFP48 [CX3007]  
MC68HC908GZ8MFJ@TQFP32 [CX3001]  
MC68HC908GZ8VFA@TQFP48 [CX3007]  
MC68HC908GZ8VFJ@TQFP32 [CX3001]  
MC68HC908JB12DW@SOIC28 [CX1033]  
MC68HC908JB12JDW@SOIC20 [CX1033]  
MC68HC908JB12JDWE@SOIC20 [CX1033]  
MC68HC908JB16DW@SOIC28 [CX1033]  
MC68HC908JB16FA@QFP32 [CX3001]  
MC68HC908JB16JDW@SOIC20 [CX1033]  
MC68HC908JB16JDWE@SOIC20 [CX1033]  
MC68HC908JB8ADW@SOIC28 [CX1033]  
MC68HC908JB8FB@TQFP44 [CX3003]  
MC68HC908JB8JDW@SOIC20 [CX1033]  
MC68HC908JB8JP  
MC68HC908JK1CDW@SOIC20 [CX1033]  
MC68HC908JK1CP  
MC68HC908JK1ECDW@SOIC20 [CX1033]  
MC68HC908JK1ECDWE@SOIC20 [CX1033]  
MC68HC908JK1ECP  
MC68HC908JK1EMDW@SOIC20 [CX1033]  
MC68HC908JK1EMDWE@SOIC20 [CX1033]  
MC68HC908JK1EMP  
MC68HC908JK1EVDW@SOIC20 [CX1033]  
MC68HC908JK1EVDWE@SOIC20 [CX1033]  
MC68HC908JK1EVP  
MC68HC908JK1MDW@SOIC20 [CX1033]  
MC68HC908JK1MP  
MC68HC908JK1VDW@SOIC20 [CX1033]  
MC68HC908JK1VP  
MC68HC908JK3CDW@SOIC20 [CX1033]  
MC68HC908JK3CP  
MC68HC908JK3ECDW@SOIC20 [CX1033]  
MC68HC908JK3ECDWE@SOIC20 [CX1033]  
MC68HC908JK3ECP  
MC68HC908JK3EMDW@SOIC20 [CX1033]  
MC68HC908JK3EMDWE@SOIC20 [CX1033]  
MC68HC908JK3EMP  
MC68HC908JK3EVDW@SOIC20 [CX1033]  
MC68HC908JK3EVDWE@SOIC20 [CX1033]  
MC68HC908GZ60CFUE@QFP64 [CX3014]  
MC68HC908GZ60MFUE@QFP64 [CX3014]  
MC68HC908GZ60VFUE@QFP64 [CX3014]  
MC68HC908GZ8CFAE@TQFP48 [CX3007]  
MC68HC908GZ8CFJE@TQFP32 [CX3001]  
MC68HC908GZ8MFAE@TQFP48 [CX3007]  
MC68HC908GZ8MFJE@TQFP32 [CX3001]  
MC68HC908GZ8VFAE@TQFP48 [CX3007]  
MC68HC908GZ8VFJE@TQFP32 [CX3001]  
MC68HC908JB12DWE@SOIC28 [CX1033]  
MC68HC908JB16DWE@SOIC28 [CX1033]  
MC68HC908JB16FAE@QFP32 [CX3001]  
MC68HC908JB8ADWE@SOIC28 [CX1033]  
MC68HC908JB8FB@TQFP44 [CX3003]  
MC68HC908JB8JDWE@SOIC20 [CX1033]  
MC68HC908JB8JPE  
MC68HC908JK1CDWE@SOIC20 [CX1033]  
MC68HC908JK1CPE  
MC68HC908JK1ECPE  
MC68HC908JK1EMPE  
MC68HC908JK1EVPE  
MC68HC908JK1MDWE@SOIC20 [CX1033]  
MC68HC908JK1MPPE  
MC68HC908JK1VDWE@SOIC20 [CX1033]  
MC68HC908JK1VPE  
MC68HC908JK3CDWE@SOIC20 [CX1033]  
MC68HC908JK3CPE  
MC68HC908JK3ECPE  
MC68HC908JK3EMPE

MC68HC908JK3EVP  
MC68HC908JK3MDW@SOIC20 [CX1033]  
MC68HC908JK3MP  
MC68HC908JK3VDW@SOIC20 [CX1033]  
MC68HC908JK3VP  
MC68HC908JK8CDW@SOIC20 [CX1033]  
MC68HC908JK8CP  
MC68HC908JK8MDW@SOIC20 [CX1033]  
MC68HC908JK8MP  
MC68HC908JK8VDW@SOIC20 [CX1033]  
MC68HC908JK8VP  
MC68HC908JL16CDW@SOIC28 [CX1033]  
MC68HC908JL16CDWE@SOIC28 [CX1033]  
MC68HC908JL16CFJ@TQFP32 [CX3001]  
MC68HC908JL16CFJE@TQFP32 [CX3001]  
MC68HC908JL16CP  
MC68HC908JL16CSP@SDIP32 [CX0032]  
MC68HC908JL16CSPE@SDIP32 [CX0032]  
MC68HC908JL16MDW@SOIC28 [CX1033]  
MC68HC908JL16MDWE@SOIC28 [CX1033]  
MC68HC908JL16MFJ@TQFP32 [CX3001]  
MC68HC908JL16MFJE@TQFP32 [CX3001]  
MC68HC908JL16MP  
MC68HC908JL16MSP@SDIP32 [CX0032]  
MC68HC908JL16MSPE@SDIP32 [CX0032]  
MC68HC908JL16VDW@SOIC28 [CX1033]  
MC68HC908JL16VDWE@SOIC28 [CX1033]  
MC68HC908JL16VFJ@TQFP32 [CX3001]  
MC68HC908JL16VFJE@TQFP32 [CX3001]  
MC68HC908JL16VP  
MC68HC908JL16VSP@SDIP32 [CX0032]  
MC68HC908JL16VSPE@SDIP32 [CX0032]  
MC68HC908JL3CDW@SOIC28 [CX1033]  
MC68HC908JL3CP  
MC68HC908JL3ECDW@SOIC28 [CX1033]  
MC68HC908JL3ECDWE@SOIC28 [CX1033]  
MC68HC908JL3ECFA@TQFP48 [CX3007]  
MC68HC908JL3ECFAE@TQFP48 [CX3007]  
MC68HC908JL3ECP  
MC68HC908JL3EMDW@SOIC28 [CX1033]  
MC68HC908JL3EMDWE@SOIC28 [CX1033]  
MC68HC908JL3EMFA@TQFP48 [CX3007]  
MC68HC908JL3EMFAE@TQFP48 [CX3007]  
MC68HC908JL3EMP  
MC68HC908JL3EVDW@SOIC28 [CX1033]  
MC68HC908JL3EVDWE@SOIC28 [CX1033]  
MC68HC908JL3EVFA@TQFP48 [CX3007]  
MC68HC908JL3EVFAE@TQFP48 [CX3007]  
MC68HC908JL3EVP  
MC68HC908JL3MDW@SOIC28 [CX1033]  
MC68HC908JL3MP  
MC68HC908JL3VDW@SOIC28 [CX1033]  
MC68HC908JL3VP  
MC68HC908JL8CDW@SOIC28 [CX1033]  
MC68HC908JL8CFA@TQFP32 [CX3001]  
MC68HC908JL8CP  
MC68HC908JL8CSP@SDIP32 [CX0032]  
MC68HC908JL8MDW@SOIC28 [CX1033]  
MC68HC908JL8MFA@TQFP32 [CX3001]

MC68HC908JK3EVP  
MC68HC908JK3MDWE@SOIC20 [CX1033]  
MC68HC908JK3MP  
MC68HC908JK3VDWE@SOIC20 [CX1033]  
MC68HC908JK3VP  
MC68HC908JK8CDWE@SOIC20 [CX1033]  
MC68HC908JK8CPE  
MC68HC908JK8MDWE@SOIC20 [CX1033]  
MC68HC908JK8MP  
MC68HC908JK8VDWE@SOIC20 [CX1033]  
MC68HC908JK8VP

MC68HC908JL16CPE

MC68HC908JL16MPE

MC68HC908JL16VPE

MC68HC908JL3CDWE@SOIC28 [CX1033]  
MC68HC908JL3CPE

MC68HC908JL3ECP

MC68HC908JL3EMPE

MC68HC908JL3EVP  
MC68HC908JL3MDWE@SOIC28 [CX1033]  
MC68HC908JL3MP  
MC68HC908JL3VDWE@SOIC28 [CX1033]  
MC68HC908JL3VP  
MC68HC908JL8CDWE@SOIC28 [CX1033]  
MC68HC908JL8CFAE@TQFP32 [CX3001]  
MC68HC908JL8CPE  
MC68HC908JL8CSPE@SDIP32 [CX0032]  
MC68HC908JL8MDWE@SOIC28 [CX1033]  
MC68HC908JL8MFAE@TQFP32 [CX3001]

MC68HC908JL8MP  
MC68HC908JL8MSP@SDIP32 [CX0032]  
MC68HC908JL8VDW@SOIC28 [CX1033]  
MC68HC908JL8VFA@TQFP32 [CX3001]  
MC68HC908JL8VP  
MC68HC908JL8VSP@SDIP32 [CX0032]  
MC68HC908KK3ECDW@SOIC20 [CX1033]  
MC68HC908KK3ECDWE@SOIC20 [CX1033]  
MC68HC908KK3ECP  
MC68HC908KK3EMDW@SOIC20 [CX1033]  
MC68HC908KK3EMDWE@SOIC20 [CX1033]  
MC68HC908KK3EMP  
MC68HC908KK3EVDW@SOIC20 [CX1033]  
MC68HC908KK3EVDWE@SOIC20 [CX1033]  
MC68HC908KK3EVP  
MC68HC908KL3ECDW@SOIC28 [CX1033]  
MC68HC908KL3ECDWE@SOIC28 [CX1033]  
MC68HC908KL3ECP  
MC68HC908KL3EMDW@SOIC28 [CX1033]  
MC68HC908KL3EMDWE@SOIC28 [CX1033]  
MC68HC908KL3EMP  
MC68HC908KL3EVDW@SOIC28 [CX1033]  
MC68HC908KL3EVDWE@SOIC28 [CX1033]  
MC68HC908KL3EVP  
MC68HC908KL8CDW@SOIC28 [CX1033]  
MC68HC908KL8CP  
MC68HC908KL8CSP@SDIP32 [CX0032]  
MC68HC908KL8MDW@SOIC28 [CX1033]  
MC68HC908KL8MP  
MC68HC908KL8MSP@SDIP32 [CX0032]  
MC68HC908KL8VDW@SOIC28 [CX1033]  
MC68HC908KL8VP  
MC68HC908KL8VSP@SDIP32 [CX0032]  
MC68HC908KX2CDW@SOIC16 [CX1033]  
MC68HC908KX2CP  
MC68HC908KX2MDW@SOIC16 [CX1033]  
MC68HC908KX2MP  
MC68HC908KX2VDW@SOIC16 [CX1033]  
MC68HC908KX8CDW@SOIC16 [CX1033]  
MC68HC908KX8CP  
MC68HC908KX8MDW@SOIC16 [CX1033]  
MC68HC908KX8MP  
MC68HC908KX8VDW@SOIC16 [CX1033]  
MC68HC908KX8VP  
MC68HC908KXVMP  
MC68HC908LB8CDW@SOIC20 [CX1033]  
MC68HC908LB8CP  
MC68HC908LB8MDW@SOIC20 [CX1033]  
MC68HC908LB8MP  
MC68HC908LB8VDW@SOIC20 [CX1033]  
MC68HC908LB8VP  
MC68HC908LD60IFU@QFP64 [CX3014]  
MC68HC908LJ12CFB@TQFP52 [CX3010]  
MC68HC908LJ12CFBE@TQFP52 [CX3010]  
MC68HC908LJ12CFU@TQFP64 [CX3014]  
MC68HC908LJ12CFUE@TQFP64 [CX3014]  
MC68HC908LJ12CPB@TQFP64 [CX3011]  
MC68HC908LJ12CPBE@TQFP64 [CX3011]  
MC68HC908LJ12MFB@TQFP52 [CX3010]

MC68HC908JL8MPPE  
MC68HC908JL8MSPE@SDIP32 [CX0032]  
MC68HC908JL8VDWE@SOIC28 [CX1033]  
MC68HC908JL8VFAE@TQFP32 [CX3001]  
MC68HC908JL8VPE  
MC68HC908JL8VSPE@SDIP32 [CX0032]  
  
MC68HC908KK3ECPPE  
  
MC68HC908KK3EMPE  
  
MC68HC908KK3EVPE  
  
MC68HC908KL3ECPPE  
  
MC68HC908KL3EMPE  
  
MC68HC908KL3EVPE  
MC68HC908KL8CDWE@SOIC28 [CX1033]  
MC68HC908KL8CPE  
MC68HC908KL8CSPE@SDIP32 [CX0032]  
MC68HC908KL8MDWE@SOIC28 [CX1033]  
MC68HC908KL8MPPE  
MC68HC908KL8MSPE@SDIP32 [CX0032]  
MC68HC908KL8VDWE@SOIC28 [CX1033]  
MC68HC908KL8VPE  
MC68HC908KL8VSPE@SDIP32 [CX0032]  
MC68HC908KX2CDWE@SOIC16 [CX1033]  
MC68HC908KX2CPE  
MC68HC908KX2MDWE@SOIC16 [CX1033]  
MC68HC908KX2MPPE  
MC68HC908KX2VDWE@SOIC16 [CX1033]  
MC68HC908KX8CDWE@SOIC16 [CX1033]  
MC68HC908KX8CPE  
MC68HC908KX8MDWE@SOIC16 [CX1033]  
MC68HC908KX8MPPE  
MC68HC908KX8VDWE@SOIC16 [CX1033]  
MC68HC908KX8VPE  
MC68HC908KXVMPPE  
MC68HC908LB8CDWE@SOIC20 [CX1033]  
MC68HC908LB8CPE  
MC68HC908LB8MDWE@SOIC20 [CX1033]  
MC68HC908LB8MPPE  
MC68HC908LB8VDWE@SOIC20 [CX1033]  
MC68HC908LB8VPE  
MC68HC908LD64IFU@QFP64 [CX3014]

MC68HC908LJ12MFBE@TQFP52 [CX3010]  
MC68HC908LJ12MFU@TQFP64 [CX3014]  
MC68HC908LJ12MFUE@TQFP64 [CX3014]  
MC68HC908LJ12MPB@TQFP64 [CX3011]  
MC68HC908LJ12MPBE@TQFP64 [CX3011]  
MC68HC908LJ12VFB@TQFP52 [CX3010]  
MC68HC908LJ12VFBE@TQFP52 [CX3010]  
MC68HC908LJ12VFU@TQFP64 [CX3014]  
MC68HC908LJ12VFUE@TQFP64 [CX3014]  
MC68HC908LJ12VPB@TQFP64 [CX3011]  
MC68HC908LJ12VPBE@TQFP64 [CX3011]  
MC68HC908LJ24CFQ@TQFP80 [CX3018]  
MC68HC908LJ24CFQE@TQFP80 [CX3018]  
MC68HC908LJ24CFU@TQFP64 [CX3014]  
MC68HC908LJ24CFUE@TQFP64 [CX3014]  
MC68HC908LJ24CPB@TQFP64 [CX3011]  
MC68HC908LJ24CPBE@TQFP64 [CX3011]  
MC68HC908LJ24CPK@TQFP80 [CX3016]  
MC68HC908LJ24CPKE@TQFP80 [CX3016]  
MC68HC908LJ24MFQ@TQFP80 [CX3018]  
MC68HC908LJ24MFQE@TQFP80 [CX3018]  
MC68HC908LJ24MFU@TQFP64 [CX3014]  
MC68HC908LJ24MFUE@TQFP64 [CX3014]  
MC68HC908LJ24MPB@TQFP64 [CX3011]  
MC68HC908LJ24MPBE@TQFP64 [CX3011]  
MC68HC908LJ24MPK@TQFP80 [CX3016]  
MC68HC908LJ24MPKE@TQFP80 [CX3016]  
MC68HC908LJ24VFQ@TQFP80 [CX3018]  
MC68HC908LJ24VFQE@TQFP80 [CX3018]  
MC68HC908LJ24VFU@TQFP64 [CX3014]  
MC68HC908LJ24VFUE@TQFP64 [CX3014]  
MC68HC908LJ24VPB@TQFP64 [CX3011]  
MC68HC908LJ24VPBE@TQFP64 [CX3011]  
MC68HC908LJ24VPK@TQFP80 [CX3016]  
MC68HC908LJ24VPKE@TQFP80 [CX3016]  
MC68HC908LK24CFQ@TQFP80 [CX3018]  
MC68HC908LK24CFQE@TQFP80 [CX3018]  
MC68HC908LK24CFU@TQFP64 [CX3014]  
MC68HC908LK24CFUE@TQFP64 [CX3014]  
MC68HC908LK24CPB@TQFP64 [CX3011]  
MC68HC908LK24CPBE@TQFP64 [CX3011]  
MC68HC908LK24CPK@TQFP80 [CX3016]  
MC68HC908LK24CPKE@TQFP80 [CX3016]  
MC68HC908LK24MFQ@TQFP80 [CX3018]  
MC68HC908LK24MFQE@TQFP80 [CX3018]  
MC68HC908LK24MFU@TQFP64 [CX3014]  
MC68HC908LK24MFUE@TQFP64 [CX3014]  
MC68HC908LK24MPB@TQFP64 [CX3011]  
MC68HC908LK24MPBE@TQFP64 [CX3011]  
MC68HC908LK24MPK@TQFP80 [CX3016]  
MC68HC908LK24MPKE@TQFP80 [CX3016]  
MC68HC908LK24VFQ@TQFP80 [CX3018]  
MC68HC908LK24VFQE@TQFP80 [CX3018]  
MC68HC908LK24VFU@TQFP64 [CX3014]  
MC68HC908LK24VFUE@TQFP64 [CX3014]  
MC68HC908LK24VPB@TQFP64 [CX3011]  
MC68HC908LK24VPBE@TQFP64 [CX3011]  
MC68HC908LK24VPK@TQFP80 [CX3016]  
MC68HC908LK24VPKE@TQFP80 [CX3016]



MC68HC908LV8CPB@TQFP52 [CX3010]      MC68HC908LV8CPBE@TQFP52 [CX3010]  
MC68HC908MR16CB@SDIP56 [CX0056]      MC68HC908MR16CBE@SDIP56 [CX0056]  
MC68HC908MR16CFU@TQFP64 [CX3014]  
MC68HC908MR16CFUE@TQFP64 [CX3014]  
MC68HC908MR16MB@SDIP56 [CX0056]      MC68HC908MR16MBE@SDIP56 [CX0056]  
MC68HC908MR16MFU@TQFP64 [CX3014]  
MC68HC908MR16MFUE@TQFP64 [CX3014]  
MC68HC908MR16VB@SDIP56 [CX0056]      MC68HC908MR16VBE@SDIP56 [CX0056]  
MC68HC908MR16VFU@TQFP64 [CX3014]  
MC68HC908MR16VFUE@TQFP64 [CX3014]  
MC68HC908MR32CB@SDIP56 [CX0056]      MC68HC908MR32CBE@SDIP56 [CX0056]  
MC68HC908MR32CFU@TQFP64 [CX3014]  
MC68HC908MR32CFUE@TQFP64 [CX3014]  
MC68HC908MR32MB@SDIP56 [CX0056]      MC68HC908MR32MBE@SDIP56 [CX0056]  
MC68HC908MR32MFU@TQFP64 [CX3014]  
MC68HC908MR32MFUE@TQFP64 [CX3014]  
MC68HC908MR32VB@SDIP56 [CX0056]      MC68HC908MR32VBE@SDIP56 [CX0056]  
MC68HC908MR32VFU@TQFP64 [CX3014]  
MC68HC908MR32VFUE@TQFP64 [CX3014]  
MC68HC908MR8CDW@SOIC28 [CX1033]      MC68HC908MR8CDWE@SOIC28 [CX1033]  
MC68HC908MR8CFA@QFP32 [CX3001]      MC68HC908MR8CFAE@QFP32 [CX3001]  
MC68HC908MR8CP      MC68HC908MR8CPE  
MC68HC908MR8MDW@SOIC28 [CX1033]      MC68HC908MR8MDWE@SOIC28 [CX1033]  
MC68HC908MR8MFA@QFP32 [CX3001]      MC68HC908MR8MFAE@QFP32 [CX3001]  
MC68HC908MR8MP      MC68HC908MR8MPE  
MC68HC908MR8VDW@SOIC28 [CX1033]      MC68HC908MR8VDWE@SOIC28 [CX1033]  
MC68HC908MR8VFA@QFP32 [CX3001]      MC68HC908MR8VFAE@QFP32 [CX3001]  
MC68HC908MR8VP      MC68HC908MR8VPE  
MC68HC908QB4CDT@TSSOP16 [CX1001]  
MC68HC908QB4CDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB4CDTE@TSSOP16 [CX1001]  
MC68HC908QB4CDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB4CDW@SOIC16 [CX1033]  
MC68HC908QB4CDW@SOIC16(a trim) [CX1033]  
MC68HC908QB4CDWE@SOIC16 [CX1033]  
MC68HC908QB4CDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB4CP      MC68HC908QB4CP(a trim)  
MC68HC908QB4CPE      MC68HC908QB4CPE(a trim)  
MC68HC908QB4MDT@TSSOP16 [CX1001]  
MC68HC908QB4MDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB4MDTE@TSSOP16 [CX1001]  
MC68HC908QB4MDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB4MDW@SOIC16 [CX1033]  
MC68HC908QB4MDW@SOIC16(a trim) [CX1033]  
MC68HC908QB4MDWE@SOIC16 [CX1033]  
MC68HC908QB4MDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB4MP      MC68HC908QB4MP(a trim)  
MC68HC908QB4MPE      MC68HC908QB4MPE(a trim)  
MC68HC908QB4VDT@TSSOP16 [CX1001]  
MC68HC908QB4VDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB4VDTE@TSSOP16 [CX1001]  
MC68HC908QB4VDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB4VDW@SOIC16 [CX1033]  
MC68HC908QB4VDW@SOIC16(a trim) [CX1033]  
MC68HC908QB4VDWE@SOIC16 [CX1033]  
MC68HC908QB4VDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB4VP      MC68HC908QB4VP(a trim)  
MC68HC908QB4VPE      MC68HC908QB4VPE(a trim)  
MC68HC908QB8CDT@TSSOP16 [CX1001]

MC68HC908QB8CDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB8CDTE@TSSOP16 [CX1001]  
MC68HC908QB8CDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB8CDW@SOIC16 [CX1033]  
MC68HC908QB8CDW@SOIC16(a trim) [CX1033]  
MC68HC908QB8CDWE@SOIC16 [CX1033]  
MC68HC908QB8CDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB8CP MC68HC908QB8CP(a trim)  
MC68HC908QB8CPE MC68HC908QB8CPE(a trim)  
MC68HC908QB8MDT@TSSOP16 [CX1001]  
MC68HC908QB8MDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB8MDTE@TSSOP16 [CX1001]  
MC68HC908QB8MDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB8MDW@SOIC16 [CX1033]  
MC68HC908QB8MDW@SOIC16(a trim) [CX1033]  
MC68HC908QB8MDWE@SOIC16 [CX1033]  
MC68HC908QB8MDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB8MP MC68HC908QB8MP(a trim)  
MC68HC908QB8MPE MC68HC908QB8MPE(a trim)  
MC68HC908QB8VDT@TSSOP16 [CX1001]  
MC68HC908QB8VDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB8VDTE@TSSOP16 [CX1001]  
MC68HC908QB8VDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB8VDW@SOIC16 [CX1033]  
MC68HC908QB8VDW@SOIC16(a trim) [CX1033]  
MC68HC908QB8VDWE@SOIC16 [CX1033]  
MC68HC908QB8VDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB8VP MC68HC908QB8VP(a trim)  
MC68HC908QB8VPE MC68HC908QB8VPE(a trim)  
MC68HC908QC16CDR@TSSOP28 [CX1001]  
MC68HC908QC16CDRE@TSSOP28 [CX1001]  
MC68HC908QC16CDS@TSSOP20 [CX1001]  
MC68HC908QC16CDSE@TSSOP20 [CX1001]  
MC68HC908QC16CDT@TSSOP16 [CX1001]  
MC68HC908QC16CDTE@TSSOP16 [CX1001]  
MC68HC908QC16CDX@SOIC16 [CX1033]  
MC68HC908QC16CDXE@SOIC16 [CX1033]  
MC68HC908QC16CDY@SOIC20 [CX1033]  
MC68HC908QC16CDYE@SOIC20 [CX1033]  
MC68HC908QC16CDZ@SOIC28 [CX1033]  
MC68HC908QC16CDZE@SOIC28 [CX1033]  
MC68HC908QC16MDR@TSSOP28 [CX1001]  
MC68HC908QC16MDRE@TSSOP28 [CX1001]  
MC68HC908QC16MDS@TSSOP20 [CX1001]  
MC68HC908QC16MDSE@TSSOP20 [CX1001]  
MC68HC908QC16MDT@TSSOP16 [CX1001]  
MC68HC908QC16MDTE@TSSOP16 [CX1001]  
MC68HC908QC16MDX@SOIC16 [CX1033]  
MC68HC908QC16MDXE@SOIC16 [CX1033]  
MC68HC908QC16MDY@SOIC20 [CX1033]  
MC68HC908QC16MDYE@SOIC20 [CX1033]  
MC68HC908QC16MDZ@SOIC28 [CX1033]  
MC68HC908QC16MDZE@SOIC28 [CX1033]  
MC68HC908QC16VDR@TSSOP28 [CX1001]  
MC68HC908QC16VDRE@TSSOP28 [CX1001]  
MC68HC908QC16VDS@TSSOP20 [CX1001]  
MC68HC908QC16VDSE@TSSOP20 [CX1001]  
MC68HC908QC16VDT@TSSOP16 [CX1001]  
MC68HC908QC16VDTE@TSSOP16 [CX1001]

MC68HC908QC16VDX@SOIC16 [CX1033]  
MC68HC908QC16VDXE@SOIC16 [CX1033]  
MC68HC908QC16VDY@SOIC20 [CX1033]  
MC68HC908QC16VDYE@SOIC20 [CX1033]  
MC68HC908QC16VDZ@SOIC28 [CX1033]  
MC68HC908QC16VDZE@SOIC28 [CX1033]  
MC68HC908QC4CDR@TSSOP28 [CX1001]  
MC68HC908QC4CDRE@TSSOP28 [CX1001]  
MC68HC908QC4CDS@TSSOP20 [CX1001]  
MC68HC908QC4CDSE@TSSOP20 [CX1001]  
MC68HC908QC4CDT@TSSOP16 [CX1001]  
MC68HC908QC4CDTE@TSSOP16 [CX1001]  
MC68HC908QC4CDX@SOIC16 [CX1033]  
MC68HC908QC4CDY@SOIC20 [CX1033]  
MC68HC908QC4CDZ@SOIC28 [CX1033]  
MC68HC908QC4MDR@TSSOP28 [CX1001]  
MC68HC908QC4MDRE@TSSOP28 [CX1001]  
MC68HC908QC4MDS@TSSOP20 [CX1001]  
MC68HC908QC4MDSE@TSSOP20 [CX1001]  
MC68HC908QC4MDT@TSSOP16 [CX1001]  
MC68HC908QC4MDTE@TSSOP16 [CX1001]  
MC68HC908QC4MDX@SOIC16 [CX1033]  
MC68HC908QC4MDY@SOIC20 [CX1033]  
MC68HC908QC4MDZ@SOIC28 [CX1033]  
MC68HC908QC4VDR@TSSOP28 [CX1001]  
MC68HC908QC4VDRE@TSSOP28 [CX1001]  
MC68HC908QC4VDS@TSSOP20 [CX1001]  
MC68HC908QC4VDSE@TSSOP20 [CX1001]  
MC68HC908QC4VDT@TSSOP16 [CX1001]  
MC68HC908QC4VDTE@TSSOP16 [CX1001]  
MC68HC908QC4VDX@SOIC16 [CX1033]  
MC68HC908QC4VDY@SOIC20 [CX1033]  
MC68HC908QC4VDZ@SOIC28 [CX1033]  
MC68HC908QC8CDR@TSSOP28 [CX1001]  
MC68HC908QC8CDRE@TSSOP28 [CX1001]  
MC68HC908QC8CDS@TSSOP20 [CX1001]  
MC68HC908QC8CDSE@TSSOP20 [CX1001]  
MC68HC908QC8CDT@TSSOP16 [CX1001]  
MC68HC908QC8CDTE@TSSOP16 [CX1001]  
MC68HC908QC8CDX@SOIC16 [CX1033]  
MC68HC908QC8CDY@SOIC20 [CX1033]  
MC68HC908QC8CDZ@SOIC28 [CX1033]  
MC68HC908QC8MDR@TSSOP28 [CX1001]  
MC68HC908QC8MDRE@TSSOP28 [CX1001]  
MC68HC908QC8MDS@TSSOP20 [CX1001]  
MC68HC908QC8MDSE@TSSOP20 [CX1001]  
MC68HC908QC8MDT@TSSOP16 [CX1001]  
MC68HC908QC8MDTE@TSSOP16 [CX1001]  
MC68HC908QC8MDX@SOIC16 [CX1033]  
MC68HC908QC8MDY@SOIC20 [CX1033]  
MC68HC908QC8MDZ@SOIC28 [CX1033]  
MC68HC908QC8VDR@TSSOP28 [CX1001]  
MC68HC908QC8VDRE@TSSOP28 [CX1001]  
MC68HC908QC8VDS@TSSOP20 [CX1001]  
MC68HC908QC8VDSE@TSSOP20 [CX1001]  
MC68HC908QC8VDT@TSSOP16 [CX1001]  
MC68HC908QC8VDTE@TSSOP16 [CX1001]  
MC68HC908QC8VDX@SOIC16 [CX1033]  
MC68HC908QC8VDY@SOIC20 [CX1033]  
MC68HC908QC4CDXE@SOIC16 [CX1033]  
MC68HC908QC4CDYE@SOIC20 [CX1033]  
MC68HC908QC4CDZE@SOIC28 [CX1033]  
MC68HC908QC4MDXE@SOIC16 [CX1033]  
MC68HC908QC4MDYE@SOIC20 [CX1033]  
MC68HC908QC4MDZE@SOIC28 [CX1033]  
MC68HC908QC4VDXE@SOIC16 [CX1033]  
MC68HC908QC4VDYE@SOIC20 [CX1033]  
MC68HC908QC4VDZE@SOIC28 [CX1033]  
MC68HC908QC8CDXE@SOIC16 [CX1033]  
MC68HC908QC8CDYE@SOIC20 [CX1033]  
MC68HC908QC8CDZE@SOIC28 [CX1033]  
MC68HC908QC8MDXE@SOIC16 [CX1033]  
MC68HC908QC8MDYE@SOIC20 [CX1033]  
MC68HC908QC8MDZE@SOIC28 [CX1033]  
MC68HC908QC8VDXE@SOIC16 [CX1033]  
MC68HC908QC8VDYE@SOIC20 [CX1033]

MC68HC908QC8VDZ@SOIC28 [CX1033]      MC68HC908QC8VDZE@SOIC28 [CX1033]  
MC68HC908QF4CFJ@QFP32 [CX3001]      MC68HC908QF4CFJE@QFP32 [CX3001]  
MC68HC908QF4MFJ@QFP32 [CX3001]      MC68HC908QF4MFJE@QFP32 [CX3001]  
MC68HC908QF4VFJ@QFP32 [CX3001]      MC68HC908QF4VFJE@QFP32 [CX3001]  
MC68HC908QL2CDT@TSSOP16 [CX1001]  
MC68HC908QL2CDTE@TSSOP16 [CX1001]  
MC68HC908QL2CDW@SOIC16 [CX1032]      MC68HC908QL2CDWE@SOIC16 [CX1032]  
MC68HC908QL2MDT@TSSOP16 [CX1001]  
MC68HC908QL2MDTE@TSSOP16 [CX1001]  
MC68HC908QL2MDW@SOIC16 [CX1032]      MC68HC908QL2MDWE@SOIC16 [CX1032]  
MC68HC908QL2VDT@TSSOP16 [CX1001]  
MC68HC908QL2VDTE@TSSOP16 [CX1001]  
MC68HC908QL2VDW@SOIC16 [CX1032]      MC68HC908QL2VDWE@SOIC16 [CX1032]  
MC68HC908QL3CDT@TSSOP16 [CX1001]  
MC68HC908QL3CDTE@TSSOP16 [CX1001]  
MC68HC908QL3CDW@SOIC16 [CX1032]      MC68HC908QL3CDWE@SOIC16 [CX1032]  
MC68HC908QL3MDT@TSSOP16 [CX1001]  
MC68HC908QL3MDTE@TSSOP16 [CX1001]  
MC68HC908QL3MDW@SOIC16 [CX1032]      MC68HC908QL3MDWE@SOIC16 [CX1032]  
MC68HC908QL3VDT@TSSOP16 [CX1001]  
MC68HC908QL3VDTE@TSSOP16 [CX1001]  
MC68HC908QL3VDW@SOIC16 [CX1032]      MC68HC908QL3VDWE@SOIC16 [CX1032]  
MC68HC908QL4CDT@TSSOP16 [CX1001]  
MC68HC908QL4CDTE@TSSOP16 [CX1001]  
MC68HC908QL4CDW@SOIC16 [CX1032]      MC68HC908QL4CDWE@SOIC16 [CX1032]  
MC68HC908QL4MDT@TSSOP16 [CX1001]  
MC68HC908QL4MDTE@TSSOP16 [CX1001]  
MC68HC908QL4MDW@SOIC16 [CX1032]      MC68HC908QL4MDWE@SOIC16 [CX1032]  
MC68HC908QL4VDT@TSSOP16 [CX1001]  
MC68HC908QL4VDTE@TSSOP16 [CX1001]  
MC68HC908QL4VDW@SOIC16 [CX1032]      MC68HC908QL4VDWE@SOIC16 [CX1032]  
MC68HC908QT1ACDW@SOIC8 [CX1032]  
MC68HC908QT1ACDW@SOIC8(a trim) [CX1032]  
MC68HC908QT1ACDWE@SOIC8 [CX1032]  
MC68HC908QT1ACDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT1ACFQ@DFN8 [CX4004]  
MC68HC908QT1ACFQ@DFN8(a trim) [CX4004]  
MC68HC908QT1ACFQE@DFN8 [CX4004]  
MC68HC908QT1ACFQE@DFN8(a trim) [CX4004]  
MC68HC908QT1ACP      MC68HC908QT1ACP(a trim)  
MC68HC908QT1ACPE      MC68HC908QT1ACPE(a trim)  
MC68HC908QT1AMDW@SOIC8 [CX1032]  
MC68HC908QT1AMDW@SOIC8(a trim) [CX1032]  
MC68HC908QT1AMDWE@SOIC8 [CX1032]  
MC68HC908QT1AMDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT1AMFQ@DFN8 [CX4004]  
MC68HC908QT1AMFQ@DFN8(a trim) [CX4004]  
MC68HC908QT1AMFQE@DFN8 [CX4004]  
MC68HC908QT1AMFQE@DFN8(a trim) [CX4004]  
MC68HC908QT1AMP      MC68HC908QT1AMP(a trim)  
MC68HC908QT1AMPE      MC68HC908QT1AMPE(a trim)  
MC68HC908QT1AVDW@SOIC8 [CX1032]  
MC68HC908QT1AVDW@SOIC8(a trim) [CX1032]  
MC68HC908QT1AVDWE@SOIC8 [CX1032]  
MC68HC908QT1AVDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT1AVFQ@DFN8 [CX4004]  
MC68HC908QT1AVFQ@DFN8(a trim) [CX4004]  
MC68HC908QT1AVFQE@DFN8 [CX4004]  
MC68HC908QT1AVFQE@DFN8(a trim) [CX4004]

MC68HC908QT1AVP	MC68HC908QT1AVP(a trim)
MC68HC908QT1AVPE	MC68HC908QT1AVPE(a trim)
MC68HC908QT1CDW@SOIC8 [CX1032]	MC68HC908QT1CDWE@SOIC8 [CX1032]
MC68HC908QT1CFQ@DFN8 [CX4004]	MC68HC908QT1CFQE@DFN8 [CX4004]
MC68HC908QT1CP	MC68HC908QT1CPE
MC68HC908QT1MDW@SOIC8 [CX1032]	MC68HC908QT1MDWE@SOIC8 [CX1032]
MC68HC908QT1MFQ@DFN8 [CX4004]	MC68HC908QT1MFQE@DFN8 [CX4004]
MC68HC908QT1MP	MC68HC908QT1MPE
MC68HC908QT1VDW@SOIC8 [CX1032]	MC68HC908QT1VDWE@SOIC8 [CX1032]
MC68HC908QT1VFQ@DFN8 [CX4004]	MC68HC908QT1VFQE@DFN8 [CX4004]
MC68HC908QT1VP	MC68HC908QT1VPE
MC68HC908QT2ACDW@SOIC8 [CX1032]	
MC68HC908QT2ACDW@SOIC8(a trim) [CX1032]	
MC68HC908QT2ACDWE@SOIC8 [CX1032]	
MC68HC908QT2ACDWE@SOIC8(a trim) [CX1032]	
MC68HC908QT2ACFQ@DFN8 [CX4004]	
MC68HC908QT2ACFQ@DFN8(a trim) [CX4004]	
MC68HC908QT2ACFQE@DFN8 [CX4004]	
MC68HC908QT2ACFQE@DFN8(a trim) [CX4004]	
MC68HC908QT2ACP	MC68HC908QT2ACP(a trim)
MC68HC908QT2ACPE	MC68HC908QT2ACPE(a trim)
MC68HC908QT2AMDW@SOIC8 [CX1032]	
MC68HC908QT2AMDW@SOIC8(a trim) [CX1032]	
MC68HC908QT2AMDWE@SOIC8 [CX1032]	
MC68HC908QT2AMDWE@SOIC8(a trim) [CX1032]	
MC68HC908QT2AMFQ@DFN8 [CX4004]	
MC68HC908QT2AMFQ@DFN8(a trim) [CX4004]	
MC68HC908QT2AMFQE@DFN8 [CX4004]	
MC68HC908QT2AMFQE@DFN8(a trim) [CX4004]	
MC68HC908QT2AMP	MC68HC908QT2AMP(a trim)
MC68HC908QT2AMPE	MC68HC908QT2AMPE(a trim)
MC68HC908QT2AVDW@SOIC8 [CX1032]	
MC68HC908QT2AVDW@SOIC8(a trim) [CX1032]	
MC68HC908QT2AVDWE@SOIC8 [CX1032]	
MC68HC908QT2AVDWE@SOIC8(a trim) [CX1032]	
MC68HC908QT2AVFQ@DFN8 [CX4004]	
MC68HC908QT2AVFQ@DFN8(a trim) [CX4004]	
MC68HC908QT2AVFQE@DFN8 [CX4004]	
MC68HC908QT2AVFQE@DFN8(a trim) [CX4004]	
MC68HC908QT2AVP	MC68HC908QT2AVP(a trim)
MC68HC908QT2AVPE	MC68HC908QT2AVPE(a trim)
MC68HC908QT2CDW@SOIC8 [CX1032]	MC68HC908QT2CDWE@SOIC8 [CX1032]
MC68HC908QT2CFQ@DFN8 [CX4004]	MC68HC908QT2CFQE@DFN8 [CX4004]
MC68HC908QT2CP	MC68HC908QT2CPE
MC68HC908QT2MDW@SOIC8 [CX1032]	MC68HC908QT2MDWE@SOIC8 [CX1032]
MC68HC908QT2MFQ@DFN8 [CX4004]	MC68HC908QT2MFQE@DFN8 [CX4004]
MC68HC908QT2MP	MC68HC908QT2MPE
MC68HC908QT2VDW@SOIC8 [CX1032]	MC68HC908QT2VDWE@SOIC8 [CX1032]
MC68HC908QT2VFQ@DFN8 [CX4004]	MC68HC908QT2VFQE@DFN8 [CX4004]
MC68HC908QT2VP	MC68HC908QT2VPE
MC68HC908QT4ACDW@SOIC8 [CX1032]	
MC68HC908QT4ACDW@SOIC8(a trim) [CX1032]	
MC68HC908QT4ACDWE@SOIC8 [CX1032]	
MC68HC908QT4ACDWE@SOIC8(a trim) [CX1032]	
MC68HC908QT4ACFQ@DFN8 [CX4004]	
MC68HC908QT4ACFQ@DFN8(a trim) [CX4004]	
MC68HC908QT4ACFQE@DFN8 [CX4004]	
MC68HC908QT4ACFQE@DFN8(a trim) [CX4004]	
MC68HC908QT4ACP	MC68HC908QT4ACP(a trim)

MC68HC908QT4ACPE MC68HC908QT4ACPE(a trim)  
MC68HC908QT4AMDW@SOIC8 [CX1032]  
MC68HC908QT4AMDW@SOIC8(a trim) [CX1032]  
MC68HC908QT4AMDWE@SOIC8 [CX1032]  
MC68HC908QT4AMDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT4AMFQ@DFN8 [CX4004]  
MC68HC908QT4AMFQ@DFN8(a trim) [CX4004]  
MC68HC908QT4AMFQE@DFN8 [CX4004]  
MC68HC908QT4AMFQE@DFN8(a trim) [CX4004]  
MC68HC908QT4AMP MC68HC908QT4AMP(a trim)  
MC68HC908QT4AMPE MC68HC908QT4AMPE(a trim)  
MC68HC908QT4AVDW@SOIC8 [CX1032]  
MC68HC908QT4AVDW@SOIC8(a trim) [CX1032]  
MC68HC908QT4AVDWE@SOIC8 [CX1032]  
MC68HC908QT4AVDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT4AVFQ@DFN8 [CX4004]  
MC68HC908QT4AVFQ@DFN8(a trim) [CX4004]  
MC68HC908QT4AVFQE@DFN8 [CX4004]  
MC68HC908QT4AVFQE@DFN8(a trim) [CX4004]  
MC68HC908QT4AVP MC68HC908QT4AVP(a trim)  
MC68HC908QT4AVPE MC68HC908QT4AVPE(a trim)  
MC68HC908QT4CDW@SOIC8 [CX1032] MC68HC908QT4CDWE@SOIC8 [CX1032]  
MC68HC908QT4CFQ@DFN8 [CX4004] MC68HC908QT4CFQE@DFN8 [CX4004]  
MC68HC908QT4CPE  
MC68HC908QT4MDW@SOIC8 [CX1032] MC68HC908QT4MDWE@SOIC8 [CX1032]  
MC68HC908QT4MFQ@DFN8 [CX4004] MC68HC908QT4MFQE@DFN8 [CX4004]  
MC68HC908QT4MPE  
MC68HC908QT4VDW@SOIC8 [CX1032] MC68HC908QT4VDWE@SOIC8 [CX1032]  
MC68HC908QT4VFQ@DFN8 [CX4004] MC68HC908QT4VFQE@DFN8 [CX4004]  
MC68HC908QT4VPE  
MC68HC908QY1ACDT@TSSOP16 [CX1001]  
MC68HC908QY1ACDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY1ACDTE@TSSOP16 [CX1001]  
MC68HC908QY1ACDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY1ACDW@SOIC16 [CX1033]  
MC68HC908QY1ACDW@SOIC16(a trim) [CX1033]  
MC68HC908QY1ACDWE@SOIC16 [CX1033]  
MC68HC908QY1ACDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY1ACP MC68HC908QY1ACP(a trim)  
MC68HC908QY1ACPE MC68HC908QY1ACPE(a trim)  
MC68HC908QY1AMDT@TSSOP16 [CX1001]  
MC68HC908QY1AMDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AMDTE@TSSOP16 [CX1001]  
MC68HC908QY1AMDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AMDW@SOIC16 [CX1033]  
MC68HC908QY1AMDW@SOIC16(a trim) [CX1033]  
MC68HC908QY1AMDWE@SOIC16 [CX1033]  
MC68HC908QY1AMDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY1AMP MC68HC908QY1AMP(a trim)  
MC68HC908QY1AMPE MC68HC908QY1AMPE(a trim)  
MC68HC908QY1AVDT@TSSOP16 [CX1001]  
MC68HC908QY1AVDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AVDTE@TSSOP16 [CX1001]  
MC68HC908QY1AVDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AVDW@SOIC16 [CX1033]  
MC68HC908QY1AVDW@SOIC16(a trim) [CX1033]  
MC68HC908QY1AVDWE@SOIC16 [CX1033]  
MC68HC908QY1AVDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY1AVP MC68HC908QY1AVP(a trim)

MC68HC908QY1AVPE	MC68HC908QY1AVPE(a trim)
MC68HC908QY1CDT@TSSOP16 [CX1001]	
MC68HC908QY1CDTE@TSSOP16 [CX1001]	
MC68HC908QY1CDW@SOIC16 [CX1033]	MC68HC908QY1CDWE@SOIC16 [CX1033]
MC68HC908QY1CP	MC68HC908QY1CPE
MC68HC908QY1MDT@TSSOP16 [CX1001]	
MC68HC908QY1MDTE@TSSOP16 [CX1001]	
MC68HC908QY1MDW@SOIC16 [CX1033]	MC68HC908QY1MDWE@SOIC16 [CX1033]
MC68HC908QY1MP	MC68HC908QY1MPE
MC68HC908QY1VDT@TSSOP16 [CX1001]	
MC68HC908QY1VDTE@TSSOP16 [CX1001]	
MC68HC908QY1VDW@SOIC16 [CX1033]	MC68HC908QY1VDWE@SOIC16 [CX1033]
MC68HC908QY1VP	MC68HC908QY1VPE
MC68HC908QY2ACDT@TSSOP16 [CX1001]	
MC68HC908QY2ACDT@TSSOP16(a trim) [CX1001]	
MC68HC908QY2ACDTE@TSSOP16 [CX1001]	
MC68HC908QY2ACDTE@TSSOP16(a trim) [CX1001]	
MC68HC908QY2ACDW@SOIC16 [CX1033]	
MC68HC908QY2ACDW@SOIC16(a trim) [CX1033]	
MC68HC908QY2ACDWE@SOIC16 [CX1033]	
MC68HC908QY2ACDWE@SOIC16(a trim) [CX1033]	
MC68HC908QY2ACP	MC68HC908QY2ACP(a trim)
MC68HC908QY2ACPE	MC68HC908QY2ACPE(a trim)
MC68HC908QY2AMDT@TSSOP16 [CX1001]	
MC68HC908QY2AMDT@TSSOP16(a trim) [CX1001]	
MC68HC908QY2AMDTE@TSSOP16 [CX1001]	
MC68HC908QY2AMDTE@TSSOP16(a trim) [CX1001]	
MC68HC908QY2AMDW@SOIC16 [CX1033]	
MC68HC908QY2AMDW@SOIC16(a trim) [CX1033]	
MC68HC908QY2AMDWE@SOIC16 [CX1033]	
MC68HC908QY2AMDWE@SOIC16(a trim) [CX1033]	
MC68HC908QY2AMP	MC68HC908QY2AMP(a trim)
MC68HC908QY2AMPE	MC68HC908QY2AMPE(a trim)
MC68HC908QY2AVDT@TSSOP16 [CX1001]	
MC68HC908QY2AVDT@TSSOP16(a trim) [CX1001]	
MC68HC908QY2AVDTE@TSSOP16 [CX1001]	
MC68HC908QY2AVDTE@TSSOP16(a trim) [CX1001]	
MC68HC908QY2AVDW@SOIC16 [CX1033]	
MC68HC908QY2AVDW@SOIC16(a trim) [CX1033]	
MC68HC908QY2AVDWE@SOIC16 [CX1033]	
MC68HC908QY2AVDWE@SOIC16(a trim) [CX1033]	
MC68HC908QY2AVP	MC68HC908QY2AVP(a trim)
MC68HC908QY2AVPE	MC68HC908QY2AVPE(a trim)
MC68HC908QY2CDT@TSSOP16 [CX1001]	
MC68HC908QY2CDTE@TSSOP16 [CX1001]	
MC68HC908QY2CDW@SOIC16 [CX1033]	MC68HC908QY2CDWE@SOIC16 [CX1033]
MC68HC908QY2CP	MC68HC908QY2CPE
MC68HC908QY2MDT@TSSOP16 [CX1001]	
MC68HC908QY2MDTE@TSSOP16 [CX1001]	
MC68HC908QY2MDW@SOIC16 [CX1033]	MC68HC908QY2MDWE@SOIC16 [CX1033]
MC68HC908QY2MP	MC68HC908QY2MPE
MC68HC908QY2VDT@TSSOP16 [CX1001]	
MC68HC908QY2VDTE@TSSOP16 [CX1001]	
MC68HC908QY2VDW@SOIC16 [CX1033]	MC68HC908QY2VDWE@SOIC16 [CX1033]
MC68HC908QY2VP	MC68HC908QY2VPE
MC68HC908QY4ACDT@TSSOP16 [CX1001]	
MC68HC908QY4ACDT@TSSOP16(a trim) [CX1001]	
MC68HC908QY4ACDTE@TSSOP16 [CX1001]	
MC68HC908QY4ACDTE@TSSOP16(a trim) [CX1001]	

MC68HC908QY4ACDW@SOIC16 [CX1033]  
MC68HC908QY4ACDW@SOIC16(a trim) [CX1033]  
MC68HC908QY4ACDWE@SOIC16 [CX1033]  
MC68HC908QY4ACDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY4ACP MC68HC908QY4ACP(a trim)  
MC68HC908QY4ACPE MC68HC908QY4ACPE(a trim)  
MC68HC908QY4AMDT@TSSOP16 [CX1001]  
MC68HC908QY4AMDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AMDTE@TSSOP16 [CX1001]  
MC68HC908QY4AMDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AMDW@SOIC16 [CX1033]  
MC68HC908QY4AMDW@SOIC16(a trim) [CX1033]  
MC68HC908QY4AMDWE@SOIC16 [CX1033]  
MC68HC908QY4AMDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY4AMP MC68HC908QY4AMP(a trim)  
MC68HC908QY4AMPE MC68HC908QY4AMPE(a trim)  
MC68HC908QY4AVDT@TSSOP16 [CX1001]  
MC68HC908QY4AVDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AVDTE@TSSOP16 [CX1001]  
MC68HC908QY4AVDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AVDW@SOIC16 [CX1033]  
MC68HC908QY4AVDW@SOIC16(a trim) [CX1033]  
MC68HC908QY4AVDWE@SOIC16 [CX1033]  
MC68HC908QY4AVDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY4AVP MC68HC908QY4AVP(a trim)  
MC68HC908QY4AVPE MC68HC908QY4AVPE(a trim)  
MC68HC908QY4CDT@TSSOP16 [CX1001]  
MC68HC908QY4CDTE@TSSOP16 [CX1001]  
MC68HC908QY4CDW@SOIC16 [CX1033] MC68HC908QY4CDWE@SOIC16 [CX1033]  
MC68HC908QY4CP MC68HC908QY4CPE  
MC68HC908QY4MDT@TSSOP16 [CX1001]  
MC68HC908QY4MDTE@TSSOP16 [CX1001]  
MC68HC908QY4MDW@SOIC16 [CX1033] MC68HC908QY4MDWE@SOIC16 [CX1033]  
MC68HC908QY4MP MC68HC908QY4MPE  
MC68HC908QY4VDT@TSSOP16 [CX1001]  
MC68HC908QY4VDTE@TSSOP16 [CX1001]  
MC68HC908QY4VDW@SOIC16 [CX1033] MC68HC908QY4VDWE@SOIC16 [CX1033]  
MC68HC908QY4VP MC68HC908QY4VPE  
MC68HC908QY8CDT@TSSOP16 [CX1001]  
MC68HC908QY8CDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY8CDTE@TSSOP16 [CX1001]  
MC68HC908QY8CDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY8CDW@SOIC16 [CX1033]  
MC68HC908QY8CDW@SOIC16(a trim) [CX1033]  
MC68HC908QY8CDWE@SOIC16 [CX1033]  
MC68HC908QY8CDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY8CP MC68HC908QY8CP(a trim)  
MC68HC908QY8CPE MC68HC908QY8CPE(a trim)  
MC68HC908QY8MDT@TSSOP16 [CX1001]  
MC68HC908QY8MDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY8MDTE@TSSOP16 [CX1001]  
MC68HC908QY8MDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY8MDW@SOIC16 [CX1033]  
MC68HC908QY8MDW@SOIC16(a trim) [CX1033]  
MC68HC908QY8MDWE@SOIC16 [CX1033]  
MC68HC908QY8MDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY8MP MC68HC908QY8MP(a trim)  
MC68HC908QY8MPE MC68HC908QY8MPE(a trim)  
MC68HC908QY8VDT@TSSOP16 [CX1001]



MC68HC908QY8VDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY8VDTE@TSSOP16 [CX1001]  
MC68HC908QY8VDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY8VDW@SOIC16 [CX1033]  
MC68HC908QY8VDW@SOIC16(a trim) [CX1033]  
MC68HC908QY8VDWE@SOIC16 [CX1033]  
MC68HC908QY8VDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY8VP MC68HC908QY8VP(a trim)  
MC68HC908QY8VPE MC68HC908QY8VPE(a trim)  
MC68HC908SR12CB@SDIP42 [CX0042] MC68HC908SR12CBE@SDIP42 [CX0042]  
MC68HC908SR12CFA@TQFP48 [CX3007]  
MC68HC908SR12CFAE@TQFP48 [CX3007]  
MC68HC908SR12MB@SDIP42 [CX0042] MC68HC908SR12MBE@SDIP42 [CX0042]  
MC68HC908SR12MFA@TQFP48 [CX3007]  
MC68HC908SR12MFAE@TQFP48 [CX3007]  
MC68HC908SR12VB@SDIP42 [CX0042] MC68HC908SR12VBE@SDIP42 [CX0042]  
MC68HC908SR12VFA@TQFP48 [CX3007]  
MC68HC908SR12VFAE@TQFP48 [CX3007]  
MC68HCP11E1@PLCC52 [CX2052] MC68HCP11E1@QFP52 [CX3010]  
MC68HCP11E1CFN2 [CX2052] MC68HCP11E1CFN3 [CX2052]  
MC68HCP11E1CFU2 [CX3044] MC68HCP11E1CFU3 [CX3044]  
MC68HCP11E1MFN2 [CX2052] MC68HCP11E1MFU2 [CX3044]  
MC68HCP11E1VFN2 [CX2052] MC68HCP11E1VFU2 [CX3044]  
MC68HLC908JK1EIDW@SOIC20 [CX1033]  
MC68HLC908JK1EIDWE@SOIC20 [CX1033]  
MC68HLC908JK1EIP MC68HLC908JK1EIP  
MC68HLC908JK3EIDW@SOIC20 [CX1033]  
MC68HLC908JK3EIDWE@SOIC20 [CX1033]  
MC68HLC908JK3EIP MC68HLC908JK3EIP  
MC68HLC908JL3EIDW@SOIC28 [CX1033]  
MC68HLC908JL3EIDWE@SOIC28 [CX1033]  
MC68HLC908JL3EIFA@TQFP48 [CX3007]  
MC68HLC908JL3EIFAE@TQFP48 [CX3007]  
MC68HLC908JL3EIP MC68HLC908JL3EIP  
MC68HRC908JK1CDW@SOIC20 [CX1033]  
MC68HRC908JK1CDWE@SOIC20 [CX1033]  
MC68HRC908JK1CP MC68HRC908JK1CP  
MC68HRC908JK1ECDW@SOIC20 [CX1033]  
MC68HRC908JK1ECDWE@SOIC20 [CX1033]  
MC68HRC908JK1ECP MC68HRC908JK1ECP  
MC68HRC908JK1EMDW@SOIC20 [CX1033]  
MC68HRC908JK1EMDWE@SOIC20 [CX1033]  
MC68HRC908JK1EMP MC68HRC908JK1EMP  
MC68HRC908JK1EVDW@SOIC20 [CX1033]  
MC68HRC908JK1EVDWE@SOIC20 [CX1033]  
MC68HRC908JK1EVP MC68HRC908JK1EVP  
MC68HRC908JK1MDW@SOIC20 [CX1033]  
MC68HRC908JK1MDWE@SOIC20 [CX1033]  
MC68HRC908JK1MP MC68HRC908JK1MP  
MC68HRC908JK1VDW@SOIC20 [CX1033]  
MC68HRC908JK1VDWE@SOIC20 [CX1033]  
MC68HRC908JK1VP MC68HRC908JK1VP  
MC68HRC908JK3CDW@SOIC20 [CX1033]  
MC68HRC908JK3CDWE@SOIC20 [CX1033]  
MC68HRC908JK3CP MC68HRC908JK3CP  
MC68HRC908JK3ECDW@SOIC20 [CX1033]  
MC68HRC908JK3ECDWE@SOIC20 [CX1033]  
MC68HRC908JK3ECP MC68HRC908JK3ECP  
MC68HRC908JK3EMDW@SOIC20 [CX1033]

MC68HRC908JK3EMDWE@SOIC20 [CX1033] MC68HRC908JK3EMPE  
MC68HRC908JK3EMP  
MC68HRC908JK3EVDW@SOIC20 [CX1033] MC68HRC908JK3EVPE  
MC68HRC908JK3EVDWE@SOIC20 [CX1033] MC68HRC908JK3EVPE  
MC68HRC908JK3EVP  
MC68HRC908JK3MDW@SOIC20 [CX1033] MC68HRC908JK3MPE  
MC68HRC908JK3MDWE@SOIC20 [CX1033] MC68HRC908JK3MPE  
MC68HRC908JK3MP  
MC68HRC908JK3VDW@SOIC20 [CX1033] MC68HRC908JK3VPE  
MC68HRC908JK3VDWE@SOIC20 [CX1033] MC68HRC908JK3VPE  
MC68HRC908JK3VP  
MC68HRC908JK3VPE  
MC68HRC908JL3CDW@SOIC28 [CX1033] MC68HRC908JL3CPE  
MC68HRC908JL3CDWE@SOIC28 [CX1033] MC68HRC908JL3CPE  
MC68HRC908JL3CP  
MC68HRC908JL3ECDW@SOIC28 [CX1033] MC68HRC908JL3ECPE  
MC68HRC908JL3ECDWE@SOIC28 [CX1033] MC68HRC908JL3ECPE  
MC68HRC908JL3ECFA@TQFP48 [CX3007] MC68HRC908JL3ECPE  
MC68HRC908JL3ECFAE@TQFP48 [CX3007] MC68HRC908JL3ECPE  
MC68HRC908JL3ECP  
MC68HRC908JL3ECP  
MC68HRC908JL3EMDWE@SOIC28 [CX1033] MC68HRC908JL3EMPE  
MC68HRC908JL3EMDWE@SOIC28 [CX1033] MC68HRC908JL3EMPE  
MC68HRC908JL3EMFA@TQFP48 [CX3007] MC68HRC908JL3EMPE  
MC68HRC908JL3EMFAE@TQFP48 [CX3007] MC68HRC908JL3EMPE  
MC68HRC908JL3EMP  
MC68HRC908JL3EMP  
MC68HRC908JL3EVDW@SOIC28 [CX1033] MC68HRC908JL3EVPE  
MC68HRC908JL3EVDWE@SOIC28 [CX1033] MC68HRC908JL3EVPE  
MC68HRC908JL3EVFA@TQFP48 [CX3007] MC68HRC908JL3EVPE  
MC68HRC908JL3EVFAE@TQFP48 [CX3007] MC68HRC908JL3EVPE  
MC68HRC908JL3EVP  
MC68HRC908JL3EVP  
MC68HRC908JL3MDW@SOIC28 [CX1033] MC68HRC908JL3MPE  
MC68HRC908JL3MDWE@SOIC28 [CX1033] MC68HRC908JL3MPE  
MC68HRC908JL3MP  
MC68HRC908JL3MP  
MC68HRC908JL3VDW@SOIC28 [CX1033] MC68HRC908JL3VPE  
MC68HRC908JL3VDWE@SOIC28 [CX1033] MC68HRC908JL3VPE  
MC68HRC908JL3VP  
MC68HRC908JL3VP  
MC68HSC705C8A [CX0001] MC68HSC705C8A@PLCC44 [CX2044]  
MC68HSC705C8A@SDIP42 [CX0042] MC68HSC705C8A@TQFP44 [CX3002]  
MC68S711E9@PLCC52 [CX2052] MC68S711E9FN@PLCC52 [CX2052]  
MC9RS08KA1CDB@DFN6 [CX4000]  
MC9RS08KA1CDB@DFN6(auto trim) [CX4000]  
MC9RS08KA1CDBE@DFN6 [CX4000]  
MC9RS08KA1CDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA1CPC MC9RS08KA1CPC(auto trim)  
MC9RS08KA1CPCE MC9RS08KA1CPCE(auto trim)  
MC9RS08KA1CSC@SOIC8 [CX1030]  
MC9RS08KA1CSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA1CSCE@SOIC8 [CX1030]  
MC9RS08KA1CSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA1MDB@DFN6 [CX4000]  
MC9RS08KA1MDB@DFN6(auto trim) [CX4000]  
MC9RS08KA1MDBE@DFN6 [CX4000]  
MC9RS08KA1MDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA1MPC MC9RS08KA1MPC(auto trim)  
MC9RS08KA1MPCE MC9RS08KA1MPCE(auto trim)  
MC9RS08KA1MSC@SOIC8 [CX1030]  
MC9RS08KA1MSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA1MSCE@SOIC8 [CX1030]  
MC9RS08KA1MSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA1VDB@DFN6 [CX4000]

MC9RS08KA1VDB@DFN6(auto trim) [CX4000]  
MC9RS08KA1VDBE@DFN6 [CX4000]  
MC9RS08KA1VDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA1VPC MC9RS08KA1VPC(auto trim)  
MC9RS08KA1VPCE MC9RS08KA1VPCE(auto trim)  
MC9RS08KA1VSC@SOIC8 [CX1030]  
MC9RS08KA1VSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA1VSCE@SOIC8 [CX1030]  
MC9RS08KA1VSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA2CDB@DFN6 [CX4000]  
MC9RS08KA2CDB@DFN6(auto trim) [CX4000]  
MC9RS08KA2CDBE@DFN6 [CX4000]  
MC9RS08KA2CDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA2CPC MC9RS08KA2CPC(auto trim)  
MC9RS08KA2CPCE MC9RS08KA2CPCE(auto trim)  
MC9RS08KA2CSC@SOIC8 [CX1030]  
MC9RS08KA2CSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA2CSCE@SOIC8 [CX1030]  
MC9RS08KA2CSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA2MDB@DFN6 [CX4000]  
MC9RS08KA2MDB@DFN6(auto trim) [CX4000]  
MC9RS08KA2MDBE@DFN6 [CX4000]  
MC9RS08KA2MDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA2MPC MC9RS08KA2MPC(auto trim)  
MC9RS08KA2MPCE MC9RS08KA2MPCE(auto trim)  
MC9RS08KA2MSC@SOIC8 [CX1030]  
MC9RS08KA2MSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA2MSCE@SOIC8 [CX1030]  
MC9RS08KA2MSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA2VDB@DFN6 [CX4000]  
MC9RS08KA2VDB@DFN6(auto trim) [CX4000]  
MC9RS08KA2VDBE@DFN6 [CX4000]  
MC9RS08KA2VDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA2VPC MC9RS08KA2VPC(auto trim)  
MC9RS08KA2VPCE MC9RS08KA2VPCE(auto trim)  
MC9RS08KA2VSC@SOIC8 [CX1030]  
MC9RS08KA2VSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA2VSCE@SOIC8 [CX1030]  
MC9RS08KA2VSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA4CPG MC9RS08KA4CPG(auto trim)  
MC9RS08KA4CPGE MC9RS08KA4CPGE(auto trim)  
MC9RS08KA4CPJ MC9RS08KA4CPJ(auto trim)  
MC9RS08KA4CPJE MC9RS08KA4CPJE(auto trim)  
MC9RS08KA4CTG@TSSOP16 [CX1001]  
MC9RS08KA4CTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4CTGE@TSSOP16 [CX1001]  
MC9RS08KA4CTGE@TSSOP16(a trim) [CX1001]  
MC9RS08KA4CWG@SOIC16 [CX1033]  
MC9RS08KA4CWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA4CWGE@SOIC16 [CX1033]  
MC9RS08KA4CWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA4CWJ@SOIC20 [CX1033]  
MC9RS08KA4CWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA4CWJE@SOIC20 [CX1033]  
MC9RS08KA4CWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA4MPG MC9RS08KA4MPG(auto trim)  
MC9RS08KA4MPGE MC9RS08KA4MPGE(auto trim)  
MC9RS08KA4MPJ MC9RS08KA4MPJ(auto trim)  
MC9RS08KA4MPJE MC9RS08KA4MPJE(auto trim)

MC9RS08KA4MTG@TSSOP16 [CX1001]  
MC9RS08KA4MTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4MTGE@TSSOP16 [CX1001]  
MC9RS08KA4MTGE@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4MWG@SOIC16 [CX1033]  
MC9RS08KA4MWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA4MWGE@SOIC16 [CX1033]  
MC9RS08KA4MWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA4MWJ@SOIC20 [CX1033]  
MC9RS08KA4MWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA4MWJE@SOIC20 [CX1033]  
MC9RS08KA4MWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA4VPG MC9RS08KA4VPG(auto trim)  
MC9RS08KA4VPGE MC9RS08KA4VPGE(auto trim)  
MC9RS08KA4VPJ MC9RS08KA4VPJ(auto trim)  
MC9RS08KA4VPJE MC9RS08KA4VPJE(auto trim)  
MC9RS08KA4VTG@TSSOP16 [CX1001]  
MC9RS08KA4VTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4VTGE@TSSOP16 [CX1001]  
MC9RS08KA4VTGE@TSSOP16(a trim) [CX1001]  
MC9RS08KA4VWG@SOIC16 [CX1033]  
MC9RS08KA4VWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA4VWGE@SOIC16 [CX1033]  
MC9RS08KA4VWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA4VWJ@SOIC20 [CX1033]  
MC9RS08KA4VWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA4VWJE@SOIC20 [CX1033]  
MC9RS08KA4VWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA8CPG MC9RS08KA8CPG(auto trim)  
MC9RS08KA8CPGE MC9RS08KA8CPGE(auto trim)  
MC9RS08KA8CPJ MC9RS08KA8CPJ(auto trim)  
MC9RS08KA8CPJE MC9RS08KA8CPJE(auto trim)  
MC9RS08KA8CTG@TSSOP16 [CX1001]  
MC9RS08KA8CTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA8CTGE@TSSOP16 [CX1001]  
MC9RS08KA8CTGE@TSSOP16(a trim) [CX1001]  
MC9RS08KA8CWG@SOIC16 [CX1033]  
MC9RS08KA8CWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA8CWGE@SOIC16 [CX1033]  
MC9RS08KA8CWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA8CWJ@SOIC20 [CX1033]  
MC9RS08KA8CWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA8CWJE@SOIC20 [CX1033]  
MC9RS08KA8CWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA8MPG MC9RS08KA8MPG(auto trim)  
MC9RS08KA8MPGE MC9RS08KA8MPGE(auto trim)  
MC9RS08KA8MPJ MC9RS08KA8MPJ(auto trim)  
MC9RS08KA8MPJE MC9RS08KA8MPJE(auto trim)  
MC9RS08KA8MTG@TSSOP16 [CX1001]  
MC9RS08KA8MTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA8MTGE@TSSOP16 [CX1001]  
MC9RS08KA8MTGE@TSSOP16(a trim) [CX1001]  
MC9RS08KA8MWG@SOIC16 [CX1033]  
MC9RS08KA8MWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA8MWGE@SOIC16 [CX1033]  
MC9RS08KA8MWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA8MWJ@SOIC20 [CX1033]  
MC9RS08KA8MWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA8MWJE@SOIC20 [CX1033]

MC9RS08KA8MWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA8VPG MC9RS08KA8VPG(auto trim)  
MC9RS08KA8VPGE MC9RS08KA8VPGE(auto trim)  
MC9RS08KA8VPJ MC9RS08KA8VPJ(auto trim)  
MC9RS08KA8VPJE MC9RS08KA8VPJE(auto trim)  
MC9RS08KA8VTG@TSSOP16 [CX1001]  
MC9RS08KA8VTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA8VTGE@TSSOP16 [CX1001]  
MC9RS08KA8VTGE@TSSOP16(a trim) [CX1001]  
MC9RS08KA8VWG@SOIC16 [CX1033]  
MC9RS08KA8VWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA8VWGE@SOIC16 [CX1033]  
MC9RS08KA8VWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA8VWJ@SOIC20 [CX1033]  
MC9RS08KA8VWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA8VWJE@SOIC20 [CX1033]  
MC9RS08KA8VWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KB12CDC@DFN8 [CX4004] MC9RS08KB12CSC@SOIC8 [CX1030]  
MC9RS08KB12CSG@SOIC16 [CX1030] MC9RS08KB12CTG@TSSOP16 [CX1001]  
MC9RS08KB12CWJ@SOIC20 [CX1033] MC9RS08KB12MDC@DFN8 [CX4004]  
MC9RS08KB12MSC@SOIC8 [CX1030] MC9RS08KB12MSG@SOIC16 [CX1030]  
MC9RS08KB12MTG@TSSOP16 [CX1001] MC9RS08KB12MWJ@SOIC20 [CX1033]  
MC9RS08KB12VDC@DFN8 [CX4004] MC9RS08KB12VSC@SOIC8 [CX1030]  
MC9RS08KB12VSG@SOIC16 [CX1030] MC9RS08KB12VTG@TSSOP16 [CX1001]  
MC9RS08KB12VWJ@SOIC20 [CX1033] MC9RS08KB2CDC@DFN8 [CX4004]  
MC9RS08KB2CSC@SOIC8 [CX1030] MC9RS08KB2CSG@SOIC16 [CX1030]  
MC9RS08KB2CTG@TSSOP16 [CX1001] MC9RS08KB2CWJ@SOIC20 [CX1033]  
MC9RS08KB2MDC@DFN8 [CX4004] MC9RS08KB2MSC@SOIC8 [CX1030]  
MC9RS08KB2MSG@SOIC16 [CX1030] MC9RS08KB2MTG@TSSOP16 [CX1001]  
MC9RS08KB2MWJ@SOIC20 [CX1033] MC9RS08KB2VDC@DFN8 [CX4004]  
MC9RS08KB2VSC@SOIC8 [CX1030] MC9RS08KB2VSG@SOIC16 [CX1030]  
MC9RS08KB2VTG@TSSOP16 [CX1001] MC9RS08KB2VWJ@SOIC20 [CX1033]  
MC9RS08KB4CDC@DFN8 [CX4004] MC9RS08KB4CSC@SOIC8 [CX1030]  
MC9RS08KB4CSG@SOIC16 [CX1030] MC9RS08KB4CTG@TSSOP16 [CX1001]  
MC9RS08KB4CWJ@SOIC20 [CX1033] MC9RS08KB4MDC@DFN8 [CX4004]  
MC9RS08KB4MSC@SOIC8 [CX1030] MC9RS08KB4MSG@SOIC16 [CX1030]  
MC9RS08KB4MTG@TSSOP16 [CX1001] MC9RS08KB4MWJ@SOIC20 [CX1033]  
MC9RS08KB4VDC@DFN8 [CX4004] MC9RS08KB4VSC@SOIC8 [CX1030]  
MC9RS08KB4VSG@SOIC16 [CX1030] MC9RS08KB4VTG@TSSOP16 [CX1001]  
MC9RS08KB4VWJ@SOIC20 [CX1033] MC9RS08KB8CDC@DFN8 [CX4004]  
MC9RS08KB8CSC@SOIC8 [CX1030] MC9RS08KB8CSG@SOIC16 [CX1030]  
MC9RS08KB8CTG@TSSOP16 [CX1001] MC9RS08KB8CWJ@SOIC20 [CX1033]  
MC9RS08KB8MDC@DFN8 [CX4004] MC9RS08KB8MSC@SOIC8 [CX1030]  
MC9RS08KB8MSG@SOIC16 [CX1030] MC9RS08KB8MTG@TSSOP16 [CX1001]  
MC9RS08KB8MWJ@SOIC20 [CX1033] MC9RS08KB8VDC@DFN8 [CX4004]  
MC9RS08KB8VSC@SOIC8 [CX1030] MC9RS08KB8VSG@SOIC16 [CX1030]  
MC9RS08KB8VTG@TSSOP16 [CX1001] MC9RS08KB8VWJ@SOIC20 [CX1033]  
MC9RS08LA8CFT@QFN48 [CX4021] MC9RS08LA8CFTE@QFN48 [CX4021]  
MC9RS08LA8CLF@QFP48 [CX3007] MC9RS08LA8CLFE@QFP48 [CX3007]  
MC9RS08LA8MFT@QFN48 [CX4021] MC9RS08LA8MFTE@QFN48 [CX4021]  
MC9RS08LA8MLF@QFP48 [CX3007] MC9RS08LA8MLFE@QFP48 [CX3007]  
MC9RS08LA8VFT@QFN48 [CX4021] MC9RS08LA8VFTE@QFN48 [CX4021]  
MC9RS08LA8VLF@QFP48 [CX3007] MC9RS08LA8VLF@QFP48 [CX3007]  
MC9RS08LE4CWL@SOIC28 [CX1033] MC9RS08LE4CWLE@SOIC28 [CX1033]  
MC9RS08LE4MWL@SOIC28 [CX1033] MC9RS08LE4MWLE@SOIC28 [CX1033]  
MC9RS08LE4VWL@SOIC28 [CX1033] MC9RS08LE4VWLE@SOIC28 [CX1033]  
MC9S08AC128CFG@QFP44 [CX3003] MC9S08AC128CFGE@QFP44 [CX3003]  
MC9S08AC128CFU@QFP64 [CX3014] MC9S08AC128CFUE@QFP64 [CX3014]  
MC9S08AC128CLK@QFP80 [CX3017] MC9S08AC128CLKE@QFP80 [CX3017]

MC9S08AC128MFG@QFP44 [CX3003]                    MC9S08AC128MFGE@QFP44 [CX3003]  
MC9S08AC128MFU@QFP64 [CX3014]                    MC9S08AC128MFUE@QFP64 [CX3014]  
MC9S08AC128MLK@QFP80 [CX3017]                    MC9S08AC128MLKE@QFP80 [CX3017]  
MC9S08AC128VFG@QFP44 [CX3003]                    MC9S08AC128VFGE@QFP44 [CX3003]  
MC9S08AC128VFU@QFP64 [CX3014]                    MC9S08AC128VFUE@QFP64 [CX3014]  
MC9S08AC128VLK@QFP80 [CX3017]                    MC9S08AC128VLKE@QFP80 [CX3017]  
MC9S08AC16CFD [CX4021]                            MC9S08AC16CFDE [CX4021]  
MC9S08AC16CFG [CX3003]  
MC9S08AC16CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16CFGE [CX3003]  
MC9S08AC16CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16CFJ [CX3001]                            MC9S08AC16CFJE [CX3001]  
MC9S08AC16MFD [CX4021]                            MC9S08AC16MFDE [CX4021]  
MC9S08AC16MFG [CX3003]  
MC9S08AC16MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16MFGE [CX3003]  
MC9S08AC16MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16MFJ [CX3001]                            MC9S08AC16MFJE [CX3001]  
MC9S08AC16VFD [CX4021]                            MC9S08AC16VFDE [CX4021]  
MC9S08AC16VFG [CX3003]  
MC9S08AC16VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16VFGE [CX3003]  
MC9S08AC16VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16VFJ [CX3001]                            MC9S08AC16VFJE [CX3001]  
MC9S08AC32CFD [CX4021]                            MC9S08AC32CFDE [CX4021]  
MC9S08AC32CFG [CX3003]  
MC9S08AC32CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32CFGE [CX3003]  
MC9S08AC32CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32CFJ [CX3001]                            MC9S08AC32CFJE [CX3001]  
MC9S08AC32CFU [CX3014]                            MC9S08AC32CFUE [CX3014]  
MC9S08AC32CPU [CX3011]                            MC9S08AC32CPUE [CX3011]  
MC9S08AC32MFD [CX4021]                            MC9S08AC32MFDE [CX4021]  
MC9S08AC32MFG [CX3003]  
MC9S08AC32MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32MFGE [CX3003]  
MC9S08AC32MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32MFJ [CX3001]                            MC9S08AC32MFJE [CX3001]  
MC9S08AC32MFU [CX3014]                            MC9S08AC32MFUE [CX3014]  
MC9S08AC32MPU [CX3011]                            MC9S08AC32MPUE [CX3011]  
MC9S08AC32VFD [CX4021]                            MC9S08AC32VFDE [CX4021]  
MC9S08AC32VFG [CX3003]  
MC9S08AC32VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32VFGE [CX3003]  
MC9S08AC32VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32VFJ [CX3001]                            MC9S08AC32VFJE [CX3001]  
MC9S08AC32VFU [CX3014]                            MC9S08AC32VFUE [CX3014]  
MC9S08AC32VPU [CX3011]                            MC9S08AC32VPUE [CX3011]  
MC9S08AC48CFD [CX4021]                            MC9S08AC48CFDE [CX4021]  
MC9S08AC48CFG [CX3003]  
MC9S08AC48CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC48CFGE [CX3003]  
MC9S08AC48CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC48CFJ [CX3001]                            MC9S08AC48CFJE [CX3001]  
MC9S08AC48CFU [CX3014]                            MC9S08AC48CFUE [CX3014]  
MC9S08AC48CPU [CX3011]                            MC9S08AC48CPUE [CX3011]  
MC9S08AC48MFD [CX4021]                            MC9S08AC48MFDE [CX4021]  
MC9S08AC48MFG [CX3003]  
MC9S08AC48MFG@LQFP44(\*) [SA245A+B4404]

MC9S08AC48MFGE [CX3003]  
MC9S08AC48MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC48MFJ [CX3001] MC9S08AC48MFJE [CX3001]  
MC9S08AC48MFU [CX3014] MC9S08AC48MFUE [CX3014]  
MC9S08AC48MPU [CX3011] MC9S08AC48MPUE [CX3011]  
MC9S08AC48VFD [CX4021] MC9S08AC48VFDE [CX4021]  
MC9S08AC48VFG [CX3003]  
MC9S08AC48VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC48VFGE [CX3003]  
MC9S08AC48VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC48VFJ [CX3001] MC9S08AC48VFJE [CX3001]  
MC9S08AC48VFU [CX3014] MC9S08AC48VFUE [CX3014]  
MC9S08AC48VPU [CX3011] MC9S08AC48VPUE [CX3011]  
MC9S08AC60CFD [CX4021] MC9S08AC60CFDE [CX4021]  
MC9S08AC60CFG [CX3003]  
MC9S08AC60CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60CFGE [CX3003]  
MC9S08AC60CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60CFJ [CX3001] MC9S08AC60CFJE [CX3001]  
MC9S08AC60CFU [CX3014] MC9S08AC60CFUE [CX3014]  
MC9S08AC60CPU [CX3011] MC9S08AC60CPUE [CX3011]  
MC9S08AC60MFD [CX4021] MC9S08AC60MFDE [CX4021]  
MC9S08AC60MFG [CX3003]  
MC9S08AC60MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60MFGE [CX3003]  
MC9S08AC60MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60MFJ [CX3001] MC9S08AC60MFJE [CX3001]  
MC9S08AC60MFU [CX3014] MC9S08AC60MFUE [CX3014]  
MC9S08AC60MPU [CX3011] MC9S08AC60MPUE [CX3011]  
MC9S08AC60VFD [CX4021] MC9S08AC60VFDE [CX4021]  
MC9S08AC60VFG [CX3003]  
MC9S08AC60VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60VFGE [CX3003]  
MC9S08AC60VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60VFJ [CX3001] MC9S08AC60VFJE [CX3001]  
MC9S08AC60VFU [CX3014] MC9S08AC60VFUE [CX3014]  
MC9S08AC60VPU [CX3011] MC9S08AC60VPUE [CX3011]  
MC9S08AC8CFD [CX4021] MC9S08AC8CFDE [CX4021]  
MC9S08AC8CFG [CX3003]  
MC9S08AC8CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8CFGE [CX3003]  
MC9S08AC8CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8CFJ [CX3001] MC9S08AC8CFJE [CX3001]  
MC9S08AC8MFD [CX4021] MC9S08AC8MFDE [CX4021]  
MC9S08AC8MFG [CX3003]  
MC9S08AC8MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8MFGE [CX3003]  
MC9S08AC8MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8MFJ [CX3001] MC9S08AC8MFJE [CX3001]  
MC9S08AC8VFD [CX4021] MC9S08AC8VFDE [CX4021]  
MC9S08AC8VFG [CX3003]  
MC9S08AC8VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8VFGE [CX3003]  
MC9S08AC8VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8VFJ [CX3001] MC9S08AC8VFJE [CX3001]  
MC9S08AC96CFG@QFP44 [CX3003] MC9S08AC96CFG@QFP44 [CX3003]  
MC9S08AC96CFU@QFP64 [CX3014] MC9S08AC96CFUE@QFP64 [CX3014]  
MC9S08AC96CLK@QFP80 [CX3017] MC9S08AC96CLKE@QFP80 [CX3017]  
MC9S08AC96MFG@QFP44 [CX3003] MC9S08AC96MFG@QFP44 [CX3003]

MC9S08AC96MFU@QFP64 [CX3014]	MC9S08AC96MFUE@QFP64 [CX3014]
MC9S08AC96MLK@QFP80 [CX3017]	MC9S08AC96MLKE@QFP80 [CX3017]
MC9S08AC96VFG@QFP44 [CX3003]	MC9S08AC96VFGE@QFP44 [CX3003]
MC9S08AC96VFU@QFP64 [CX3014]	MC9S08AC96VFUE@QFP64 [CX3014]
MC9S08AC96VLK@QFP80 [CX3017]	MC9S08AC96VLKE@QFP80 [CX3017]
MC9S08AW16CFD [CX4021]	MC9S08AW16CFDE [CX4021]
MC9S08AW16CFG [CX3003]	
MC9S08AW16CFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW16CFGE [CX3003]	
MC9S08AW16CFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW16CFU [CX3014]	MC9S08AW16CFUE [CX3014]
MC9S08AW16CPU [CX3011]	MC9S08AW16CPUE [CX3011]
MC9S08AW16MFD [CX4021]	MC9S08AW16MFDE [CX4021]
MC9S08AW16MFG [CX3003]	
MC9S08AW16MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW16MFG [CX3003]	
MC9S08AW16MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW16MFU [CX3014]	MC9S08AW16MFUE [CX3014]
MC9S08AW16MPU [CX3011]	MC9S08AW16MPUE [CX3011]
MC9S08AW16VFD [CX4021]	MC9S08AW16VFDE [CX4021]
MC9S08AW16VFG [CX3003]	
MC9S08AW16VFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW16VFGE [CX3003]	
MC9S08AW16VFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW16VFU [CX3014]	MC9S08AW16VFUE [CX3014]
MC9S08AW16VPU [CX3011]	MC9S08AW16VPUE [CX3011]
MC9S08AW32CFD [CX4021]	MC9S08AW32CFDE [CX4021]
MC9S08AW32CFG [CX3003]	
MC9S08AW32CFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW32CFGE [CX3003]	
MC9S08AW32CFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW32CFU [CX3014]	MC9S08AW32CFUE [CX3014]
MC9S08AW32CPU [CX3011]	MC9S08AW32CPUE [CX3011]
MC9S08AW32MFD [CX4021]	MC9S08AW32MFDE [CX4021]
MC9S08AW32MFG [CX3003]	
MC9S08AW32MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW32MFG [CX3003]	
MC9S08AW32MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW32MFU [CX3014]	MC9S08AW32MFUE [CX3014]
MC9S08AW32MPU [CX3011]	MC9S08AW32MPUE [CX3011]
MC9S08AW32VFD [CX4021]	MC9S08AW32VFDE [CX4021]
MC9S08AW32VFG [CX3003]	
MC9S08AW32VFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW32VFGE [CX3003]	
MC9S08AW32VFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW32VFU [CX3014]	MC9S08AW32VFUE [CX3014]
MC9S08AW32VPU [CX3011]	MC9S08AW32VPUE [CX3011]
MC9S08AW48CFD [CX4021]	MC9S08AW48CFDE [CX4021]
MC9S08AW48CFG [CX3003]	
MC9S08AW48CFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW48CFGE [CX3003]	
MC9S08AW48CFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW48CFU [CX3014]	MC9S08AW48CFUE [CX3014]
MC9S08AW48CPU [CX3011]	MC9S08AW48CPUE [CX3011]
MC9S08AW48MFD [CX4021]	MC9S08AW48MFDE [CX4021]
MC9S08AW48MFG [CX3003]	
MC9S08AW48MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW48MFG [CX3003]	
MC9S08AW48MFG@LQFP44(*) [SA245A+B4404]	



MC9S08AW48MFU [CX3014]	MC9S08AW48MFUE [CX3014]
MC9S08AW48MPU [CX3011]	MC9S08AW48MPUE [CX3011]
MC9S08AW48VFD [CX4021]	MC9S08AW48VFDE [CX4021]
MC9S08AW48VFG [CX3003]	
MC9S08AW48VFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW48VFGE [CX3003]	
MC9S08AW48VFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW48VFU [CX3014]	MC9S08AW48VFUE [CX3014]
MC9S08AW48VPU [CX3011]	MC9S08AW48VPUE [CX3011]
MC9S08AW60CFD [CX4021]	MC9S08AW60CFDE [CX4021]
MC9S08AW60CFG [CX3003]	
MC9S08AW60CFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW60CFGE [CX3003]	
MC9S08AW60CFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW60CFU [CX3014]	MC9S08AW60CFUE [CX3014]
MC9S08AW60CPU [CX3011]	MC9S08AW60CPUE [CX3011]
MC9S08AW60MFD [CX4021]	MC9S08AW60MFDE [CX4021]
MC9S08AW60MFG [CX3003]	
MC9S08AW60MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW60MFGE [CX3003]	
MC9S08AW60MFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW60MFU [CX3014]	MC9S08AW60MFUE [CX3014]
MC9S08AW60MPU [CX3011]	MC9S08AW60MPUE [CX3011]
MC9S08AW60VFD [CX4021]	MC9S08AW60VFDE [CX4021]
MC9S08AW60VFG [CX3003]	
MC9S08AW60VFG@LQFP44(*) [SA245A+B4404]	
MC9S08AW60VFGE [CX3003]	
MC9S08AW60VFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AW60VFU [CX3014]	MC9S08AW60VFUE [CX3014]
MC9S08AW60VPU [CX3011]	MC9S08AW60VPUE [CX3011]
MC9S08DN16CLC@QFP32 [CX3001]	MC9S08DN16CLCE@QFP32 [CX3001]
MC9S08DN16CLF@QFP48 [CX3007]	MC9S08DN16CLFE@QFP48 [CX3007]
MC9S08DN16CLH@QFP64 [CX3011]	MC9S08DN16CLHE@QFP64 [CX3011]
MC9S08DN16MLC@QFP32 [CX3001]	MC9S08DN16MLCE@QFP32 [CX3001]
MC9S08DN16MLF@QFP48 [CX3007]	MC9S08DN16MLFE@QFP48 [CX3007]
MC9S08DN16MLH@QFP64 [CX3011]	MC9S08DN16MLHE@QFP64 [CX3011]
MC9S08DN16VLC@QFP32 [CX3001]	MC9S08DN16VLCE@QFP32 [CX3001]
MC9S08DN16VLF@QFP48 [CX3007]	MC9S08DN16VLFE@QFP48 [CX3007]
MC9S08DN16VLH@QFP64 [CX3011]	MC9S08DN16VLHE@QFP64 [CX3011]
MC9S08DN32CLC@QFP32 [CX3001]	MC9S08DN32CLCE@QFP32 [CX3001]
MC9S08DN32CLF@QFP48 [CX3007]	MC9S08DN32CLFE@QFP48 [CX3007]
MC9S08DN32CLH@QFP64 [CX3011]	MC9S08DN32CLHE@QFP64 [CX3011]
MC9S08DN32MLC@QFP32 [CX3001]	MC9S08DN32MLCE@QFP32 [CX3001]
MC9S08DN32MLF@QFP48 [CX3007]	MC9S08DN32MLFE@QFP48 [CX3007]
MC9S08DN32MLH@QFP64 [CX3011]	MC9S08DN32MLHE@QFP64 [CX3011]
MC9S08DN32VLC@QFP32 [CX3001]	MC9S08DN32VLCE@QFP32 [CX3001]
MC9S08DN32VLF@QFP48 [CX3007]	MC9S08DN32VLFE@QFP48 [CX3007]
MC9S08DN32VLH@QFP64 [CX3011]	MC9S08DN32VLHE@QFP64 [CX3011]
MC9S08DN48CLC@QFP32 [CX3001]	MC9S08DN48CLCE@QFP32 [CX3001]
MC9S08DN48CLF@QFP48 [CX3007]	MC9S08DN48CLFE@QFP48 [CX3007]
MC9S08DN48CLH@QFP64 [CX3011]	MC9S08DN48CLHE@QFP64 [CX3011]
MC9S08DN48MLC@QFP32 [CX3001]	MC9S08DN48MLCE@QFP32 [CX3001]
MC9S08DN48MLF@QFP48 [CX3007]	MC9S08DN48MLFE@QFP48 [CX3007]
MC9S08DN48MLH@QFP64 [CX3011]	MC9S08DN48MLHE@QFP64 [CX3011]
MC9S08DN48VLC@QFP32 [CX3001]	MC9S08DN48VLCE@QFP32 [CX3001]
MC9S08DN48VLF@QFP48 [CX3007]	MC9S08DN48VLFE@QFP48 [CX3007]
MC9S08DN48VLH@QFP64 [CX3011]	MC9S08DN48VLHE@QFP64 [CX3011]
MC9S08DN60CLC@QFP32 [CX3001]	MC9S08DN60CLCE@QFP32 [CX3001]
MC9S08DN60CLF@QFP48 [CX3007]	MC9S08DN60CLFE@QFP48 [CX3007]



MC9S08DV96VLH@QFP64 [CX3011]  
MC9S08DV96VLL@QFP100 [CX3021]  
MC9S08DZ128CLF@QFP48 [CX3007]  
MC9S08DZ128CLH@QFP64 [CX3011]  
MC9S08DZ128CLL@QFP100 [CX3021]  
MC9S08DZ128MLF@QFP48 [CX3007]  
MC9S08DZ128MLH@QFP64 [CX3011]  
MC9S08DZ128MLL@QFP100 [CX3021]  
MC9S08DZ128VLF@QFP48 [CX3007]  
MC9S08DZ128VLH@QFP64 [CX3011]  
MC9S08DZ128VLL@QFP100 [CX3021]  
MC9S08DZ16CLC@QFP32 [CX3001]  
MC9S08DZ16CLF@QFP48 [CX3007]  
MC9S08DZ16CLH@QFP64 [CX3011]  
MC9S08DZ16MLC@QFP32 [CX3001]  
MC9S08DZ16MLF@QFP48 [CX3007]  
MC9S08DZ16MLH@QFP64 [CX3011]  
MC9S08DZ16VLC@QFP32 [CX3001]  
MC9S08DZ16VLF@QFP48 [CX3007]  
MC9S08DZ16VLH@QFP64 [CX3011]  
MC9S08DZ32CLC@QFP32 [CX3001]  
MC9S08DZ32CLF@QFP48 [CX3007]  
MC9S08DZ32CLH@QFP64 [CX3011]  
MC9S08DZ32MLC@QFP32 [CX3001]  
MC9S08DZ32MLF@QFP48 [CX3007]  
MC9S08DZ32MLH@QFP64 [CX3011]  
MC9S08DZ32VLC@QFP32 [CX3001]  
MC9S08DZ32VLF@QFP48 [CX3007]  
MC9S08DZ32VLH@QFP64 [CX3011]  
MC9S08DZ48CLC@QFP32 [CX3001]  
MC9S08DZ48CLF@QFP48 [CX3007]  
MC9S08DZ48CLH@QFP64 [CX3011]  
MC9S08DZ48MLC@QFP32 [CX3001]  
MC9S08DZ48MLF@QFP48 [CX3007]  
MC9S08DZ48MLH@QFP64 [CX3011]  
MC9S08DZ48VLC@QFP32 [CX3001]  
MC9S08DZ48VLF@QFP48 [CX3007]  
MC9S08DZ48VLH@QFP64 [CX3011]  
MC9S08DZ60CLC@QFP32 [CX3001]  
MC9S08DZ60CLF@QFP48 [CX3007]  
MC9S08DZ60CLH@QFP64 [CX3011]  
MC9S08DZ60MLC@QFP32 [CX3001]  
MC9S08DZ60MLF@QFP48 [CX3007]  
MC9S08DZ60MLH@QFP64 [CX3011]  
MC9S08DZ60VLC@QFP32 [CX3001]  
MC9S08DZ60VLF@QFP48 [CX3007]  
MC9S08DZ60VLH@QFP64 [CX3011]  
MC9S08DZ96CLF@QFP48 [CX3007]  
MC9S08DZ96CLH@QFP64 [CX3011]  
MC9S08DZ96CLL@QFP100 [CX3021]  
MC9S08DZ96MLF@QFP48 [CX3007]  
MC9S08DZ96MLH@QFP64 [CX3011]  
MC9S08DZ96MLL@QFP100 [CX3021]  
MC9S08DZ96VLF@QFP48 [CX3007]  
MC9S08DZ96VLH@QFP64 [CX3011]  
MC9S08DZ96VLL@QFP100 [CX3021]  
MC9S08EL16CTJ@TSSOP20 [CX1000]  
MC9S08EL16CTL@TSSOP28 [CX1001]  
MC9S08EL16MTJ@TSSOP20 [CX1000]

MC9S08DV96VLHE@QFP64 [CX3011]  
MC9S08DV96VLL@QFP100 [CX3021]  
MC9S08DZ128CLFE@QFP48 [CX3007]  
MC9S08DZ128CLHE@QFP64 [CX3011]  
MC9S08DZ128CLLE@QFP100 [CX3021]  
MC9S08DZ128MLFE@QFP48 [CX3007]  
MC9S08DZ128MLHE@QFP64 [CX3011]  
MC9S08DZ128MLLE@QFP100 [CX3021]  
MC9S08DZ128VLF@QFP48 [CX3007]  
MC9S08DZ128VLHE@QFP64 [CX3011]  
MC9S08DZ128VLL@QFP100 [CX3021]  
MC9S08DZ16CLCE@QFP32 [CX3001]  
MC9S08DZ16CLFE@QFP48 [CX3007]  
MC9S08DZ16CLHE@QFP64 [CX3011]  
MC9S08DZ16MLCE@QFP32 [CX3001]  
MC9S08DZ16MLFE@QFP48 [CX3007]  
MC9S08DZ16MLHE@QFP64 [CX3011]  
MC9S08DZ16VLC@QFP32 [CX3001]  
MC9S08DZ16VLF@QFP48 [CX3007]  
MC9S08DZ16VLHE@QFP64 [CX3011]  
MC9S08DZ32CLCE@QFP32 [CX3001]  
MC9S08DZ32CLFE@QFP48 [CX3007]  
MC9S08DZ32CLHE@QFP64 [CX3011]  
MC9S08DZ32MLCE@QFP32 [CX3001]  
MC9S08DZ32MLFE@QFP48 [CX3007]  
MC9S08DZ32MLHE@QFP64 [CX3011]  
MC9S08DZ32VLC@QFP32 [CX3001]  
MC9S08DZ32VLF@QFP48 [CX3007]  
MC9S08DZ32VLHE@QFP64 [CX3011]  
MC9S08DZ48CLCE@QFP32 [CX3001]  
MC9S08DZ48CLFE@QFP48 [CX3007]  
MC9S08DZ48CLHE@QFP64 [CX3011]  
MC9S08DZ48MLCE@QFP32 [CX3001]  
MC9S08DZ48MLFE@QFP48 [CX3007]  
MC9S08DZ48MLHE@QFP64 [CX3011]  
MC9S08DZ48VLC@QFP32 [CX3001]  
MC9S08DZ48VLF@QFP48 [CX3007]  
MC9S08DZ48VLHE@QFP64 [CX3011]  
MC9S08DZ60CLCE@QFP32 [CX3001]  
MC9S08DZ60CLFE@QFP48 [CX3007]  
MC9S08DZ60CLHE@QFP64 [CX3011]  
MC9S08DZ60MLCE@QFP32 [CX3001]  
MC9S08DZ60MLFE@QFP48 [CX3007]  
MC9S08DZ60MLHE@QFP64 [CX3011]  
MC9S08DZ60VLC@QFP32 [CX3001]  
MC9S08DZ60VLF@QFP48 [CX3007]  
MC9S08DZ60VLHE@QFP64 [CX3011]  
MC9S08DZ96CLFE@QFP48 [CX3007]  
MC9S08DZ96CLHE@QFP64 [CX3011]  
MC9S08DZ96CLLE@QFP100 [CX3021]  
MC9S08DZ96MLFE@QFP48 [CX3007]  
MC9S08DZ96MLHE@QFP64 [CX3011]  
MC9S08DZ96MLLE@QFP100 [CX3021]  
MC9S08DZ96VLF@QFP48 [CX3007]  
MC9S08DZ96VLHE@QFP64 [CX3011]  
MC9S08DZ96VLL@QFP100 [CX3021]  
MC9S08EL16CTJE@TSSOP20 [CX1000]  
MC9S08EL16CTLE@TSSOP28 [CX1001]  
MC9S08EL16MTJE@TSSOP20 [CX1000]

MC9S08EL16MTL@TSSOP28 [CX1001]	MC9S08EL16MTLE@TSSOP28 [CX1001]
MC9S08EL16VTJ@TSSOP20 [CX1000]	MC9S08EL16VTJE@TSSOP20 [CX1000]
MC9S08EL16VTL@TSSOP28 [CX1001]	MC9S08EL16VTLE@TSSOP28 [CX1001]
MC9S08EL32CTJ@TSSOP20 [CX1000]	MC9S08EL32CTJE@TSSOP20 [CX1000]
MC9S08EL32CTL@TSSOP28 [CX1001]	MC9S08EL32CTLE@TSSOP28 [CX1001]
MC9S08EL32MTJ@TSSOP20 [CX1000]	MC9S08EL32MTJE@TSSOP20 [CX1000]
MC9S08EL32MTL@TSSOP28 [CX1001]	MC9S08EL32MTLE@TSSOP28 [CX1001]
MC9S08EL32VTJ@TSSOP20 [CX1000]	MC9S08EL32VTJE@TSSOP20 [CX1000]
MC9S08EL32VTL@TSSOP28 [CX1001]	MC9S08EL32VTLE@TSSOP28 [CX1001]
MC9S08FL16CBM@SDIP32 [CX0032]	
MC9S08FL16CBM@SDIP32(auto trim) [CX0032]	
MC9S08FL16CLC@LQFP32 [CX3001]	
MC9S08FL16CLC@LQFP32(auto trim) [CX3001]	
MC9S08FL16MBM@SDIP32 [CX0032]	
MC9S08FL16MBM@SDIP32(auto trim) [CX0032]	
MC9S08FL16MLC@LQFP32 [CX3001]	
MC9S08FL16MLC@LQFP32(auto trim) [CX3001]	
MC9S08FL16VBM@SDIP32 [CX0032]	
MC9S08FL16VBM@SDIP32(auto trim) [CX0032]	
MC9S08FL16VLC@LQFP32 [CX3001]	
MC9S08FL16VLC@LQFP32(auto trim) [CX3001]	
MC9S08FL8CBM@SDIP32 [CX0032]	
MC9S08FL8CBM@SDIP32(auto trim) [CX0032]	
MC9S08FL8CLC@LQFP32 [CX3001]	
MC9S08FL8CLC@LQFP32(auto trim) [CX3001]	
MC9S08FL8MBM@SDIP32 [CX0032]	
MC9S08FL8MBM@SDIP32(auto trim) [CX0032]	
MC9S08FL8MLC@LQFP32 [CX3001]	
MC9S08FL8MLC@LQFP32(auto trim) [CX3001]	
MC9S08FL8VBM@SDIP32 [CX0032]	
MC9S08FL8VBM@SDIP32(auto trim) [CX0032]	
MC9S08FL8VLC@LQFP32 [CX3001]	
MC9S08FL8VLC@LQFP32(auto trim) [CX3001]	
MC9S08GB32ACFU@LQFP64 [CX3011]	MC9S08GB32ACFUE@LQFP64 [CX3011]
MC9S08GB32AMFU@LQFP64 [CX3011]	MC9S08GB32AMFUE@LQFP64 [CX3011]
MC9S08GB32AVFU@LQFP64 [CX3011]	MC9S08GB32AVFUE@LQFP64 [CX3011]
MC9S08GB32CFU@LQFP64 [CX3011]	MC9S08GB32CFUE@LQFP64 [CX3011]
MC9S08GB32MFU@LQFP64 [CX3011]	MC9S08GB32MFUE@LQFP64 [CX3011]
MC9S08GB32VFU@LQFP64 [CX3011]	MC9S08GB32VFUE@LQFP64 [CX3011]
MC9S08GB60ACFU@LQFP64 [CX3011]	MC9S08GB60ACFUE@LQFP64 [CX3011]
MC9S08GB60AMFU@LQFP64 [CX3011]	MC9S08GB60AMFUE@LQFP64 [CX3011]
MC9S08GB60AVFU@LQFP64 [CX3011]	MC9S08GB60AVFUE@LQFP64 [CX3011]
MC9S08GB60CFU@LQFP64 [CX3011]	MC9S08GB60CFUE@LQFP64 [CX3011]
MC9S08GB60MFU@LQFP64 [CX3011]	MC9S08GB60MFUE@LQFP64 [CX3011]
MC9S08GB60VFU@LQFP64 [CX3011]	MC9S08GB60VFUE@LQFP64 [CX3011]
MC9S08GT16ACB@SDIP42 [CX0042]	MC9S08GT16ACBE@SDIP42 [CX0042]
MC9S08GT16ACFB@LQFP44 [CX3002]	MC9S08GT16ACFBE@LQFP44 [CX3002]
MC9S08GT16ACFC@MLF32 [CX4015]	MC9S08GT16ACFCE@MLF32 [CX4015]
MC9S08GT16ACFD@QFN48 [CX4021]	MC9S08GT16ACFDE@QFN48 [CX4021]
MC9S08GT16AMB@SDIP42 [CX0042]	MC9S08GT16AMBE@SDIP42 [CX0042]
MC9S08GT16AMFB@LQFP44 [CX3002]	MC9S08GT16AMFBE@LQFP44 [CX3002]
MC9S08GT16AMFC@MLF32 [CX4015]	MC9S08GT16AMFCE@MLF32 [CX4015]
MC9S08GT16AMFD@QFN48 [CX4021]	MC9S08GT16AMFDE@QFN48 [CX4021]
MC9S08GT16AVB@SDIP42 [CX0042]	MC9S08GT16AVBE@SDIP42 [CX0042]
MC9S08GT16AVFB@LQFP44 [CX3002]	MC9S08GT16AVFBE@LQFP44 [CX3002]
MC9S08GT16AVFC@MLF32 [CX4015]	MC9S08GT16AVFCE@MLF32 [CX4015]
MC9S08GT16AVFD@QFN48 [CX4021]	MC9S08GT16AVFDE@QFN48 [CX4021]
MC9S08GT16CB@SDIP42 [CX0042]	MC9S08GT16CBE@SDIP42 [CX0042]
MC9S08GT16CFB@LQFP44 [CX3002]	MC9S08GT16CFBE@LQFP44 [CX3002]

MC9S08GT16CFD@QFN48 [CX4021]      MC9S08GT16CFDE@QFN48 [CX4021]  
MC9S08GT16MB@SDIP42 [CX0042]      MC9S08GT16MBE@SDIP42 [CX0042]  
MC9S08GT16MFB@LQFP44 [CX3002]      MC9S08GT16MFB@LQFP44 [CX3002]  
MC9S08GT16MFD@QFN48 [CX4021]      MC9S08GT16MFDE@QFN48 [CX4021]  
MC9S08GT16VB@SDIP42 [CX0042]      MC9S08GT16VBE@SDIP42 [CX0042]  
MC9S08GT16VFB@LQFP44 [CX3002]      MC9S08GT16VFB@LQFP44 [CX3002]  
MC9S08GT16VFD@QFN48 [CX4021]      MC9S08GT16VFDE@QFN48 [CX4021]  
MC9S08GT32ACB@SDIP42 [CX0042]      MC9S08GT32ACBE@SDIP42 [CX0042]  
MC9S08GT32ACFB@LQFP44 [CX3002]      MC9S08GT32ACFBE@LQFP44 [CX3002]  
MC9S08GT32ACFD@QFN48 [CX4021]      MC9S08GT32ACFDE@QFN48 [CX4021]  
MC9S08GT32AMB@SDIP42 [CX0042]      MC9S08GT32AMBE@SDIP42 [CX0042]  
MC9S08GT32AMFB@LQFP44 [CX3002]      MC9S08GT32AMFBE@LQFP44 [CX3002]  
MC9S08GT32AMFD@QFN48 [CX4021]      MC9S08GT32AMFDE@QFN48 [CX4021]  
MC9S08GT32AVB@SDIP42 [CX0042]      MC9S08GT32AVBE@SDIP42 [CX0042]  
MC9S08GT32AVFB@LQFP44 [CX3002]      MC9S08GT32AVFBE@LQFP44 [CX3002]  
MC9S08GT32AVFD@QFN48 [CX4021]      MC9S08GT32AVFDE@QFN48 [CX4021]  
MC9S08GT32CB@SDIP42 [CX0042]      MC9S08GT32CBE@SDIP42 [CX0042]  
MC9S08GT32CFB@LQFP44 [CX3002]      MC9S08GT32CFBE@LQFP44 [CX3002]  
MC9S08GT32CFD@QFN48 [CX4021]      MC9S08GT32CFDE@QFN48 [CX4021]  
MC9S08GT32MB@SDIP42 [CX0042]      MC9S08GT32MBE@SDIP42 [CX0042]  
MC9S08GT32MFB@LQFP44 [CX3002]      MC9S08GT32MFB@LQFP44 [CX3002]  
MC9S08GT32MFD@QFN48 [CX4021]      MC9S08GT32MFDE@QFN48 [CX4021]  
MC9S08GT32VB@SDIP42 [CX0042]      MC9S08GT32VBE@SDIP42 [CX0042]  
MC9S08GT32VFB@LQFP44 [CX3002]      MC9S08GT32VFB@LQFP44 [CX3002]  
MC9S08GT32VFD@QFN48 [CX4021]      MC9S08GT32VFDE@QFN48 [CX4021]  
MC9S08GT60ACB@SDIP42 [CX0042]      MC9S08GT60ACBE@SDIP42 [CX0042]  
MC9S08GT60ACFB@LQFP44 [CX3002]      MC9S08GT60ACFBE@LQFP44 [CX3002]  
MC9S08GT60ACFD@QFN48 [CX4021]      MC9S08GT60ACFDE@QFN48 [CX4021]  
MC9S08GT60AMB@SDIP42 [CX0042]      MC9S08GT60AMBE@SDIP42 [CX0042]  
MC9S08GT60AMFB@LQFP44 [CX3002]      MC9S08GT60AMFBE@LQFP44 [CX3002]  
MC9S08GT60AMFD@QFN48 [CX4021]      MC9S08GT60AMFDE@QFN48 [CX4021]  
MC9S08GT60AVB@SDIP42 [CX0042]      MC9S08GT60AVBE@SDIP42 [CX0042]  
MC9S08GT60AVFB@LQFP44 [CX3002]      MC9S08GT60AVFBE@LQFP44 [CX3002]  
MC9S08GT60AVFD@QFN48 [CX4021]      MC9S08GT60AVFDE@QFN48 [CX4021]  
MC9S08GT60CB@SDIP42 [CX0042]      MC9S08GT60CBE@SDIP42 [CX0042]  
MC9S08GT60CFB@LQFP44 [CX3002]      MC9S08GT60CFBE@LQFP44 [CX3002]  
MC9S08GT60CFD@QFN48 [CX4021]      MC9S08GT60CFDE@QFN48 [CX4021]  
MC9S08GT60MB@SDIP42 [CX0042]      MC9S08GT60MBE@SDIP42 [CX0042]  
MC9S08GT60MFB@LQFP44 [CX3002]      MC9S08GT60MFB@LQFP44 [CX3002]  
MC9S08GT60MFD@QFN48 [CX4021]      MC9S08GT60MFDE@QFN48 [CX4021]  
MC9S08GT60VB@SDIP42 [CX0042]      MC9S08GT60VBE@SDIP42 [CX0042]  
MC9S08GT60VFB@LQFP44 [CX3002]      MC9S08GT60VFB@LQFP44 [CX3002]  
MC9S08GT60VFD@QFN48 [CX4021]      MC9S08GT60VFDE@QFN48 [CX4021]  
MC9S08GT8ACB@SDIP42 [CX0042]      MC9S08GT8ACBE@SDIP42 [CX0042]  
MC9S08GT8ACFB@LQFP44 [CX3002]      MC9S08GT8ACFBE@LQFP44 [CX3002]  
MC9S08GT8ACFC@MLF32 [CX4015]      MC9S08GT8ACFCE@MLF32 [CX4015]  
MC9S08GT8ACFD@QFN48 [CX4021]      MC9S08GT8ACFDE@QFN48 [CX4021]  
MC9S08GT8AMB@SDIP42 [CX0042]      MC9S08GT8AMBE@SDIP42 [CX0042]  
MC9S08GT8AMFB@LQFP44 [CX3002]      MC9S08GT8AMFBE@LQFP44 [CX3002]  
MC9S08GT8AMFC@MLF32 [CX4015]      MC9S08GT8AMFCE@MLF32 [CX4015]  
MC9S08GT8AMFD@QFN48 [CX4021]      MC9S08GT8AMFDE@QFN48 [CX4021]  
MC9S08GT8AVB@SDIP42 [CX0042]      MC9S08GT8AVBE@SDIP42 [CX0042]  
MC9S08GT8AVFB@LQFP44 [CX3002]      MC9S08GT8AVFBE@LQFP44 [CX3002]  
MC9S08GT8AVFC@MLF32 [CX4015]      MC9S08GT8AVFCE@MLF32 [CX4015]  
MC9S08GT8AVFD@QFN48 [CX4021]      MC9S08GT8AVFDE@QFN48 [CX4021]  
MC9S08JE128CLH@QFP64 [CX3011]      MC9S08JE128CLK@QFP80 [CX3016]  
MC9S08JE128MLH@QFP64 [CX3011]      MC9S08JE128MLK@QFP80 [CX3016]  
MC9S08JE128VLH@QFP64 [CX3011]      MC9S08JE128VLK@QFP80 [CX3016]  
MC9S08JE64CLH@QFP64 [CX3011]      MC9S08JE64MLH@QFP64 [CX3011]

MC9S08JE64VLH@QFP64 [CX3011]  
MC9S08JM16CGTE@QFN48 [CX4021]  
MC9S08JM16CLCE@QFP32 [CX3001]  
MC9S08JM16CLDE@QFP44 [CX3003]  
MC9S08JM16MGTE@QFN48 [CX4021]  
MC9S08JM16MLCE@QFP32 [CX3001]  
MC9S08JM16MLDE@QFP44 [CX3003]  
MC9S08JM16VGT@QFN48 [CX4021]  
MC9S08JM16VLC@QFP32 [CX3001]  
MC9S08JM16VLDE@QFP44 [CX3003]  
MC9S08JM32CGTE@QFN48 [CX4021]  
MC9S08JM32CLDE@QFP44 [CX3003]  
MC9S08JM32CLHE@QFP64 [CX3011]  
MC9S08JM32CQHE@QFP64 [CX3014]  
MC9S08JM32MGTE@QFN48 [CX4021]  
MC9S08JM32MLDE@QFP44 [CX3003]  
MC9S08JM32MLHE@QFP64 [CX3011]  
MC9S08JM32MQHE@QFP64 [CX3014]  
MC9S08JM32VGT@QFN48 [CX4021]  
MC9S08JM32VLD@QFP44 [CX3003]  
MC9S08JM32VLDE@QFP44 [CX3003]  
MC9S08JM32VLHE@QFP64 [CX3011]  
MC9S08JM32VQHE@QFP64 [CX3014]  
MC9S08JM60CGTE@QFN48 [CX4021]  
MC9S08JM60CLDE@QFP44 [CX3003]  
MC9S08JM60CLHE@QFP64 [CX3011]  
MC9S08JM60CQHE@QFP64 [CX3014]  
MC9S08JM60MGTE@QFN48 [CX4021]  
MC9S08JM60MLDE@QFP44 [CX3003]  
MC9S08JM60MLHE@QFP64 [CX3011]  
MC9S08JM60MQHE@QFP64 [CX3014]  
MC9S08JM60VGT@QFN48 [CX4021]  
MC9S08JM60VLD@QFP44 [CX3003]  
MC9S08JM60VLDE@QFP44 [CX3003]  
MC9S08JM60VLHE@QFP64 [CX3011]  
MC9S08JM60VQHE@QFP64 [CX3014]  
MC9S08JM8CGTE@QFN48 [CX4021]  
MC9S08JM8CLCE@QFP32 [CX3001]  
MC9S08JM8CLDE@QFP44 [CX3003]  
MC9S08JM8MGTE@QFN48 [CX4021]  
MC9S08JM8MLCE@QFP32 [CX3001]  
MC9S08JM8MLDE@QFP44 [CX3003]  
MC9S08JM8VGT@QFN48 [CX4021]  
MC9S08JM8VLC@QFP32 [CX3001]  
MC9S08JM8VLD@QFP44 [CX3003]  
MC9S08JS16CWJ@SOIC20 [CX1033]  
MC9S08JS16LCWJ@SOIC20 [CX1033]  
MC9S08JS16LMWJ@SOIC20 [CX1033]  
MC9S08JS16LVWJ@SOIC20 [CX1033]  
MC9S08JS16MWJ@SOIC20 [CX1033]  
MC9S08JS16VWJ@SOIC20 [CX1033]  
MC9S08JS8CWJ@SOIC20 [CX1033]  
MC9S08JS8LCWJ@SOIC20 [CX1033]  
MC9S08JS8LMWJ@SOIC20 [CX1033]  
MC9S08JS8LVWJ@SOIC20 [CX1033]  
MC9S08JS8MWJ@SOIC20 [CX1033]  
MC9S08JS8VWJ@SOIC20 [CX1033]  
MC9S08LC36LHE@QFP64 [CX3011]  
MC9S08LC36LKE@QFP80 [CX3016]  
MC9S08LC60LHE@QFP64 [CX3011]  
MC9S08LC60LKE@QFP80 [CX3016]

MC9S08JM16CGT@QFN48 [CX4021]  
MC9S08JM16CLC@QFP32 [CX3001]  
MC9S08JM16CLD@QFP44 [CX3003]  
MC9S08JM16MGT@QFN48 [CX4021]  
MC9S08JM16MLC@QFP32 [CX3001]  
MC9S08JM16MLD@QFP44 [CX3003]  
MC9S08JM16VGT@QFN48 [CX4021]  
MC9S08JM16VLC@QFP32 [CX3001]  
MC9S08JM16VLD@QFP44 [CX3003]  
MC9S08JM32CGT@QFN48 [CX4021]  
MC9S08JM32CLD@QFP44 [CX3003]  
MC9S08JM32CLH@QFP64 [CX3011]  
MC9S08JM32CQH@QFP64 [CX3014]  
MC9S08JM32MGT@QFN48 [CX4021]  
MC9S08JM32MLD@QFP44 [CX3003]  
MC9S08JM32MLH@QFP64 [CX3011]  
MC9S08JM32MQH@QFP64 [CX3014]  
MC9S08JM32VGT@QFN48 [CX4021]  
MC9S08JM32VLD@QFP44 [CX3003]  
MC9S08JM32VLH@QFP64 [CX3011]  
MC9S08JM32VQH@QFP64 [CX3014]  
MC9S08JM60CGT@QFN48 [CX4021]  
MC9S08JM60CLD@QFP44 [CX3003]  
MC9S08JM60CLH@QFP64 [CX3011]  
MC9S08JM60CQH@QFP64 [CX3014]  
MC9S08JM60MGT@QFN48 [CX4021]  
MC9S08JM60MLD@QFP44 [CX3003]  
MC9S08JM60MLH@QFP64 [CX3011]  
MC9S08JM60MQH@QFP64 [CX3014]  
MC9S08JM60VGT@QFN48 [CX4021]  
MC9S08JM60VLD@QFP44 [CX3003]  
MC9S08JM60VLH@QFP64 [CX3011]  
MC9S08JM60VQH@QFP64 [CX3014]  
MC9S08JM8CGT@QFN48 [CX4021]  
MC9S08JM8CLC@QFP32 [CX3001]  
MC9S08JM8CLD@QFP44 [CX3003]  
MC9S08JM8MGT@QFN48 [CX4021]  
MC9S08JM8MLC@QFP32 [CX3001]  
MC9S08JM8MLD@QFP44 [CX3003]  
MC9S08JM8VGT@QFN48 [CX4021]  
MC9S08JM8VLC@QFP32 [CX3001]  
MC9S08JM8VLD@QFP44 [CX3003]  
MC9S08JS16CFK@QFN24 [CX4034]  
MC9S08JS16LCFK@QFN24 [CX4034]  
MC9S08JS16LMFK@QFN24 [CX4034]  
MC9S08JS16LVFK@QFN24 [CX4034]  
MC9S08JS16MFK@QFN24 [CX4034]  
MC9S08JS16VFK@QFN24 [CX4034]  
MC9S08JS8CFK@QFN24 [CX4034]  
MC9S08JS8LCFK@QFN24 [CX4034]  
MC9S08JS8LMFK@QFN24 [CX4034]  
MC9S08JS8LVFK@QFN24 [CX4034]  
MC9S08JS8MFK@QFN24 [CX4034]  
MC9S08JS8VFK@QFN24 [CX4034]  
MC9S08LC36LH@QFP64 [CX3011]  
MC9S08LC36LK@QFP80 [CX3016]  
MC9S08LC60LH@QFP64 [CX3011]  
MC9S08LC60LK@QFP80 [CX3016]  
MC9S08LG16CLF@QFP48 [CX3007]

MC9S08LG16CLF@QFP48(auto trim) [CX3007]  
MC9S08LG16CLFE@QFP48 [CX3007]  
MC9S08LG16CLFE@QFP48(auto trim) [CX3007]  
MC9S08LG16CLH@QFP64 [CX3011]  
MC9S08LG16CLH@QFP64(auto trim) [CX3011]  
MC9S08LG16CLHE@QFP64 [CX3011]  
MC9S08LG16CLHE@QFP64(auto trim) [CX3011]  
MC9S08LG16MLF@QFP48 [CX3007]  
MC9S08LG16MLF@QFP48(auto trim) [CX3007]  
MC9S08LG16MLFE@QFP48 [CX3007]  
MC9S08LG16MLFE@QFP48(auto trim) [CX3007]  
MC9S08LG16MLH@QFP64 [CX3011]  
MC9S08LG16MLH@QFP64(auto trim) [CX3011]  
MC9S08LG16MLHE@QFP64 [CX3011]  
MC9S08LG16MLHE@QFP64(auto trim) [CX3011]  
MC9S08LG16VLF@QFP48 [CX3007]  
MC9S08LG16VLF@QFP48(auto trim) [CX3007]  
MC9S08LG16VLFE@QFP48 [CX3007]  
MC9S08LG16VLFE@QFP48(auto trim) [CX3007]  
MC9S08LG16VLH@QFP64 [CX3011]  
MC9S08LG16VLH@QFP64(auto trim) [CX3011]  
MC9S08LG16VLHE@QFP64 [CX3011]  
MC9S08LG16VLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32CLF@QFP48 [CX3007]  
MC9S08LG32CLF@QFP48(auto trim) [CX3007]  
MC9S08LG32CLFE@QFP48 [CX3007]  
MC9S08LG32CLFE@QFP48(auto trim) [CX3007]  
MC9S08LG32CLH@QFP64 [CX3011]  
MC9S08LG32CLH@QFP64(auto trim) [CX3011]  
MC9S08LG32CLHE@QFP64 [CX3011]  
MC9S08LG32CLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32CLK@QFP80 [CX3017]  
MC9S08LG32CLK@QFP80(auto trim) [CX3017]  
MC9S08LG32CLKE@QFP80 [CX3017]  
MC9S08LG32CLKE@QFP80(auto trim) [CX3017]  
MC9S08LG32MLF@QFP48 [CX3007]  
MC9S08LG32MLF@QFP48(auto trim) [CX3007]  
MC9S08LG32MLFE@QFP48 [CX3007]  
MC9S08LG32MLFE@QFP48(auto trim) [CX3007]  
MC9S08LG32MLH@QFP64 [CX3011]  
MC9S08LG32MLH@QFP64(auto trim) [CX3011]  
MC9S08LG32MLHE@QFP64 [CX3011]  
MC9S08LG32MLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32MLK@QFP80 [CX3017]  
MC9S08LG32MLK@QFP80(auto trim) [CX3017]  
MC9S08LG32MLKE@QFP80 [CX3017]  
MC9S08LG32MLKE@QFP80(auto trim) [CX3017]  
MC9S08LG32VLF@QFP48 [CX3007]  
MC9S08LG32VLF@QFP48(auto trim) [CX3007]  
MC9S08LG32VLFE@QFP48 [CX3007]  
MC9S08LG32VLFE@QFP48(auto trim) [CX3007]  
MC9S08LG32VLH@QFP64 [CX3011]  
MC9S08LG32VLH@QFP64(auto trim) [CX3011]  
MC9S08LG32VLHE@QFP64 [CX3011]  
MC9S08LG32VLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32VLK@QFP80 [CX3017]  
MC9S08LG32VLK@QFP80(auto trim) [CX3017]  
MC9S08LG32VLKE@QFP80 [CX3017]  
MC9S08LG32VLKE@QFP80(auto trim) [CX3017]

MC9S08LL16CGT@QFN48 [CX4021]  
MC9S08LL16CGT@QFN48(auto trim) [CX4021]  
MC9S08LL16CLF@LQFP48 [CX3007]  
MC9S08LL16CLF@LQFP48(auto trim) [CX3007]  
MC9S08LL16CLH@LQFP64 [CX3011]  
MC9S08LL16CLH@LQFP64(auto trim) [CX3011]  
MC9S08LL16MGT@QFN48 [CX4021]  
MC9S08LL16MGT@QFN48(auto trim) [CX4021]  
MC9S08LL16MLF@LQFP48 [CX3007]  
MC9S08LL16MLF@LQFP48(auto trim) [CX3007]  
MC9S08LL16MLH@LQFP64 [CX3011]  
MC9S08LL16MLH@LQFP64(auto trim) [CX3011]  
MC9S08LL16VGT@QFN48 [CX4021]  
MC9S08LL16VGT@QFN48(auto trim) [CX4021]  
MC9S08LL16VLF@LQFP48 [CX3007]  
MC9S08LL16VLF@LQFP48(auto trim) [CX3007]  
MC9S08LL16VLH@LQFP64 [CX3011]  
MC9S08LL16VLH@LQFP64(auto trim) [CX3011]  
MC9S08LL64CLH@LQFP64 [CX3011]                   MC9S08LL64CLK@QFP80 [CX3017]  
MC9S08LL64MLH@LQFP64 [CX3011]                   MC9S08LL64MLK@QFP80 [CX3017]  
MC9S08LL64VLH@LQFP64 [CX3011]                   MC9S08LL64VLK@QFP80 [CX3017]  
MC9S08LL8CGT@QFN48 [CX4021]  
MC9S08LL8CGT@QFN48(auto trim) [CX4021]  
MC9S08LL8CLF@LQFP48 [CX3007]  
MC9S08LL8CLF@LQFP48(auto trim) [CX3007]  
MC9S08LL8CLH@LQFP64 [CX3011]  
MC9S08LL8CLH@LQFP64(auto trim) [CX3011]  
MC9S08LL8MGT@QFN48 [CX4021]  
MC9S08LL8MGT@QFN48(auto trim) [CX4021]  
MC9S08LL8MLF@LQFP48 [CX3007]  
MC9S08LL8MLF@LQFP48(auto trim) [CX3007]  
MC9S08LL8MLH@LQFP64 [CX3011]  
MC9S08LL8MLH@LQFP64(auto trim) [CX3011]  
MC9S08LL8VGT@QFN48 [CX4021]  
MC9S08LL8VGT@QFN48(auto trim) [CX4021]  
MC9S08LL8VLF@LQFP48 [CX3007]  
MC9S08LL8VLF@LQFP48(auto trim) [CX3007]  
MC9S08LL8VLH@LQFP64 [CX3011]  
MC9S08LL8VLH@LQFP64(auto trim) [CX3011]  
MC9S08PA16CLC [CX3001]                   MC9S08PA16CLD [CX3005]  
MC9S08PA16CTG [CX1000]                   MC9S08PA16CTJ [CX1000]  
MC9S08PA16CWJ [CX1033]                   MC9S08PA16VLC [CX3001]  
MC9S08PA16VLD [CX3005]                   MC9S08PA16VTG [CX1000]  
MC9S08PA16VTJ [CX1000]                   MC9S08PA16VWJ [CX1033]  
MC9S08PA32CLC [CX3001]                   MC9S08PA32CLD [CX3005]  
MC9S08PA32CLF [CX3007]                   MC9S08PA32CLH [CX3011]  
MC9S08PA32CQH [CX3014]                   MC9S08PA32VLC [CX3001]  
MC9S08PA32VLD [CX3005]                   MC9S08PA32VLF [CX3007]  
MC9S08PA32VLH [CX3011]                   MC9S08PA32VQH [CX3014]  
MC9S08PA60CLC [CX3001]                   MC9S08PA60CLD [CX3005]  
MC9S08PA60CLF [CX3007]                   MC9S08PA60CLH [CX3011]  
MC9S08PA60CQH [CX3014]                   MC9S08PA60VLC [CX3001]  
MC9S08PA60VLD [CX3005]                   MC9S08PA60VLF [CX3007]  
MC9S08PA60VLH [CX3011]                   MC9S08PA60VQH [CX3014]  
MC9S08PA8CLC [CX3001]                   MC9S08PA8CLD [CX3005]  
MC9S08PA8CTG [CX1000]                   MC9S08PA8CTJ [CX1000]  
MC9S08PA8CWJ [CX1033]                   MC9S08PA8VLC [CX3001]  
MC9S08PA8VLD [CX3005]                   MC9S08PA8VTG [CX1000]  
MC9S08PA8VTJ [CX1000]                   MC9S08PA8VWJ [CX1033]



MC9S08PT16CLC [CX3001]  
MC9S08PT16CTG [CX1000]  
MC9S08PT16CWJ [CX1033]  
MC9S08PT16VLD [CX3005]  
MC9S08PT16VTJ [CX1000]  
MC9S08PT32CLC [CX3001]  
MC9S08PT32CLF [CX3007]  
MC9S08PT32CQH [CX3014]  
MC9S08PT32VLD [CX3005]  
MC9S08PT32VLH [CX3011]  
MC9S08PT60CLC [CX3001]  
MC9S08PT60CLF [CX3007]  
MC9S08PT60CQH [CX3014]  
MC9S08PT60VLD [CX3005]  
MC9S08PT60VLH [CX3011]  
MC9S08PT8CLC [CX3001]  
MC9S08PT8CTG [CX1000]  
MC9S08PT8CWJ [CX1033]  
MC9S08PT8VLD [CX3005]  
MC9S08PT8VTJ [CX1000]  
MC9S08QA2CDN@SOIC8 [CX1030]  
MC9S08QA2CFQ@DFN8 [CX4004]  
MC9S08QA2CPA  
MC9S08QA2MDN@SOIC8 [CX1030]  
MC9S08QA2MFQ@DFN8 [CX4004]  
MC9S08QA2MPA  
MC9S08QA2VDN@SOIC8 [CX1030]  
MC9S08QA2VFQ@DFN8 [CX4004]  
MC9S08QA2VPA  
MC9S08QA4CDN@SOIC8 [CX1030]  
MC9S08QA4CFQ@DFN8 [CX4004]  
MC9S08QA4CPA  
MC9S08QA4MDN@SOIC8 [CX1030]  
MC9S08QA4MFQ@DFN8 [CX4004]  
MC9S08QA4MPA  
MC9S08QA4VDN@SOIC8 [CX1030]  
MC9S08QA4VFQ@DFN8 [CX4004]  
MC9S08QA4VPA  
MC9S08QB4CGK@QFN24 [CX4034]  
MC9S08QB4CWL@SOIC28 [CX1033]  
MC9S08QB4MTG@TSSOP16 [CX1001]  
MC9S08QB4VGK@QFN24 [CX4034]  
MC9S08QB4VWL@SOIC28 [CX1033]  
MC9S08QB8CTG@TSSOP16 [CX1001]  
MC9S08QB8MGK@QFN24 [CX4034]  
MC9S08QB8MWL@SOIC28 [CX1033]  
MC9S08QB8VTG@TSSOP16 [CX1001]  
MC9S08QD2CPC  
MC9S08QD2CSC@SOIC8 [CX1016]  
MC9S08QD2MPC  
MC9S08QD2MSC@SOIC8 [CX1016]  
MC9S08QD2VPC  
MC9S08QD2VSC@SOIC8 [CX1016]  
MC9S08QD4CPC  
MC9S08QD4CSC@SOIC8 [CX1016]  
MC9S08QD4MPC  
MC9S08QD4MSC@SOIC8 [CX1016]  
MC9S08QD4VPC  
MC9S08QD4VSC@SOIC8 [CX1016]

MC9S08PT16CLD [CX3005]  
MC9S08PT16CTJ [CX1000]  
MC9S08PT16VLC [CX3001]  
MC9S08PT16VTG [CX1000]  
MC9S08PT16VWJ [CX1033]  
MC9S08PT32CLD [CX3005]  
MC9S08PT32CLH [CX3011]  
MC9S08PT32VLC [CX3001]  
MC9S08PT32VLF [CX3007]  
MC9S08PT32VQH [CX3014]  
MC9S08PT60CLD [CX3005]  
MC9S08PT60CLH [CX3011]  
MC9S08PT60VLC [CX3001]  
MC9S08PT60VLF [CX3007]  
MC9S08PT60VQH [CX3014]  
MC9S08PT8CLD [CX3005]  
MC9S08PT8CTJ [CX1000]  
MC9S08PT8VLC [CX3001]  
MC9S08PT8VTG [CX1000]  
MC9S08PT8VWJ [CX1033]  
MC9S08QA2CDNE@SOIC8 [CX1030]  
MC9S08QA2CFQE@DFN8 [CX4004]  
MC9S08QA2CPAE  
MC9S08QA2MDNE@SOIC8 [CX1030]  
MC9S08QA2MFQE@DFN8 [CX4004]  
MC9S08QA2MPAE  
MC9S08QA2VDNE@SOIC8 [CX1030]  
MC9S08QA2VFQE@DFN8 [CX4004]  
MC9S08QA2VPAE  
MC9S08QA4CDNE@SOIC8 [CX1030]  
MC9S08QA4CFQE@DFN8 [CX4004]  
MC9S08QA4CPAE  
MC9S08QA4MDNE@SOIC8 [CX1030]  
MC9S08QA4MFQE@DFN8 [CX4004]  
MC9S08QA4MPAE  
MC9S08QA4VDNE@SOIC8 [CX1030]  
MC9S08QA4VFQE@DFN8 [CX4004]  
MC9S08QA4VPAE  
MC9S08QB4CTG@TSSOP16 [CX1001]  
MC9S08QB4MGK@QFN24 [CX4034]  
MC9S08QB4MWL@SOIC28 [CX1033]  
MC9S08QB4VTG@TSSOP16 [CX1001]  
MC9S08QB8CGK@QFN24 [CX4034]  
MC9S08QB8CWL@SOIC28 [CX1033]  
MC9S08QB8MTG@TSSOP16 [CX1001]  
MC9S08QB8VGK@QFN24 [CX4034]  
MC9S08QB8VWL@SOIC28 [CX1033]  
MC9S08QD2CPCE  
MC9S08QD2CSCE@SOIC8 [CX1016]  
MC9S08QD2MPCE  
MC9S08QD2MSCE@SOIC8 [CX1016]  
MC9S08QD2VPCE  
MC9S08QD2VSCE@SOIC8 [CX1016]  
MC9S08QD4CPCE  
MC9S08QD4CSCE@SOIC8 [CX1016]  
MC9S08QD4MPCE  
MC9S08QD4MSCE@SOIC8 [CX1016]  
MC9S08QD4VPCE  
MC9S08QD4VSCE@SOIC8 [CX1016]

MC9S08QE128CFT@QFN48 [CX4021]                    MC9S08QE128CFTE@QFN48 [CX4021]  
MC9S08QE128CLC@QFP32 [CX3001]                    MC9S08QE128CLCE@QFP32 [CX3001]  
MC9S08QE128CLD@QFP44 [CX3005]                    MC9S08QE128CLDE@QFP44 [CX3005]  
MC9S08QE128CLH@QFP64 [CX3011]                    MC9S08QE128CLHE@QFP64 [CX3011]  
MC9S08QE128CLK@QFP80 [CX3017]                    MC9S08QE128CLKE@QFP80 [CX3017]  
MC9S08QE128MFT@QFN48 [CX4021]                    MC9S08QE128MFTE@QFN48 [CX4021]  
MC9S08QE128MLC@QFP32 [CX3001]                    MC9S08QE128MLCE@QFP32 [CX3001]  
MC9S08QE128MLD@QFP44 [CX3005]                    MC9S08QE128MLDE@QFP44 [CX3005]  
MC9S08QE128MLH@QFP64 [CX3011]                    MC9S08QE128MLHE@QFP64 [CX3011]  
MC9S08QE128MLK@QFP80 [CX3017]                    MC9S08QE128MLKE@QFP80 [CX3017]  
MC9S08QE128VFT@QFN48 [CX4021]                    MC9S08QE128VFTE@QFN48 [CX4021]  
MC9S08QE128VLC@QFP32 [CX3001]                    MC9S08QE128VLCE@QFP32 [CX3001]  
MC9S08QE128VLD@QFP44 [CX3005]                    MC9S08QE128VLDE@QFP44 [CX3005]  
MC9S08QE128VLH@QFP64 [CX3011]                    MC9S08QE128VLHE@QFP64 [CX3011]  
MC9S08QE128VLK@QFP80 [CX3017]                    MC9S08QE128VLKE@QFP80 [CX3017]  
MC9S08QE16CFT@QFN48 [CX4021]  
MC9S08QE16CFT@QFN48(auto trim) [CX4021]  
MC9S08QE16CFTE@QFN48 [CX4021]  
MC9S08QE16CFTE@QFN48(auto trim) [CX4021]  
MC9S08QE16CLC@QFP32 [CX3001]  
MC9S08QE16CLC@QFP32(auto trim) [CX3001]  
MC9S08QE16CLCE@QFP32 [CX3001]  
MC9S08QE16CLCE@QFP32(auto trim) [CX3001]  
MC9S08QE16CLD@QFP44 [CX3005]  
MC9S08QE16CLD@QFP44(auto trim) [CX3005]  
MC9S08QE16CLDE@QFP44 [CX3005]  
MC9S08QE16CLDE@QFP44(auto trim) [CX3005]  
MC9S08QE16CWL@SOIC28 [CX1033]  
MC9S08QE16CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE16CWLE@SOIC28 [CX1033]  
MC9S08QE16CWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE16MFT@QFN48 [CX4021]  
MC9S08QE16MFT@QFN48(auto trim) [CX4021]  
MC9S08QE16MFTE@QFN48 [CX4021]  
MC9S08QE16MFTE@QFN48(auto trim) [CX4021]  
MC9S08QE16MLC@QFP32 [CX3001]  
MC9S08QE16MLC@QFP32(auto trim) [CX3001]  
MC9S08QE16MLCE@QFP32 [CX3001]  
MC9S08QE16MLCE@QFP32(auto trim) [CX3001]  
MC9S08QE16MLD@QFP44 [CX3005]  
MC9S08QE16MLD@QFP44(auto trim) [CX3005]  
MC9S08QE16MLDE@QFP44 [CX3005]  
MC9S08QE16MLDE@QFP44(auto trim) [CX3005]  
MC9S08QE16MWL@SOIC28 [CX1033]  
MC9S08QE16MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE16MWLE@SOIC28 [CX1033]  
MC9S08QE16MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE16VFT@QFN48 [CX4021]  
MC9S08QE16VFT@QFN48(auto trim) [CX4021]  
MC9S08QE16VFTE@QFN48 [CX4021]  
MC9S08QE16VFTE@QFN48(auto trim) [CX4021]  
MC9S08QE16VLC@QFP32 [CX3001]  
MC9S08QE16VLC@QFP32(auto trim) [CX3001]  
MC9S08QE16VLCE@QFP32 [CX3001]  
MC9S08QE16VLCE@QFP32(auto trim) [CX3001]  
MC9S08QE16VLD@QFP44 [CX3005]  
MC9S08QE16VLD@QFP44(auto trim) [CX3005]  
MC9S08QE16VLDE@QFP44 [CX3005]  
MC9S08QE16VLDE@QFP44(auto trim) [CX3005]

MC9S08QE16VWL@SOIC28 [CX1033]  
MC9S08QE16VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE16VWLE@SOIC28 [CX1033]  
MC9S08QE16VWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE32CFT@QFN48 [CX4021]  
MC9S08QE32CFT@QFN48(auto trim) [CX4021]  
MC9S08QE32CFTE@QFN48 [CX4021]  
MC9S08QE32CFTE@QFN48(auto trim) [CX4021]  
MC9S08QE32CLC@QFP32 [CX3001]  
MC9S08QE32CLC@QFP32(auto trim) [CX3001]  
MC9S08QE32CLCE@QFP32 [CX3001]  
MC9S08QE32CLCE@QFP32(auto trim) [CX3001]  
MC9S08QE32CLD@QFP44 [CX3005]  
MC9S08QE32CLD@QFP44(auto trim) [CX3005]  
MC9S08QE32CLDE@QFP44 [CX3005]  
MC9S08QE32CLDE@QFP44(auto trim) [CX3005]  
MC9S08QE32CWL@SOIC28 [CX1033]  
MC9S08QE32CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE32CWLE@SOIC28 [CX1033]  
MC9S08QE32CWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE32MFT@QFN48 [CX4021]  
MC9S08QE32MFT@QFN48(auto trim) [CX4021]  
MC9S08QE32MFTE@QFN48 [CX4021]  
MC9S08QE32MFTE@QFN48(auto trim) [CX4021]  
MC9S08QE32MLC@QFP32 [CX3001]  
MC9S08QE32MLC@QFP32(auto trim) [CX3001]  
MC9S08QE32MLCE@QFP32 [CX3001]  
MC9S08QE32MLCE@QFP32(auto trim) [CX3001]  
MC9S08QE32MLD@QFP44 [CX3005]  
MC9S08QE32MLD@QFP44(auto trim) [CX3005]  
MC9S08QE32MLDE@QFP44 [CX3005]  
MC9S08QE32MLDE@QFP44(auto trim) [CX3005]  
MC9S08QE32MWL@SOIC28 [CX1033]  
MC9S08QE32MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE32MWLE@SOIC28 [CX1033]  
MC9S08QE32MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE32VFT@QFN48 [CX4021]  
MC9S08QE32VFT@QFN48(auto trim) [CX4021]  
MC9S08QE32VFTE@QFN48 [CX4021]  
MC9S08QE32VFTE@QFN48(auto trim) [CX4021]  
MC9S08QE32VLC@QFP32 [CX3001]  
MC9S08QE32VLC@QFP32(auto trim) [CX3001]  
MC9S08QE32VLCE@QFP32 [CX3001]  
MC9S08QE32VLCE@QFP32(auto trim) [CX3001]  
MC9S08QE32VLD@QFP44 [CX3005]  
MC9S08QE32VLD@QFP44(auto trim) [CX3005]  
MC9S08QE32VLDE@QFP44 [CX3005]  
MC9S08QE32VLDE@QFP44(auto trim) [CX3005]  
MC9S08QE32VWL@SOIC28 [CX1033]  
MC9S08QE32VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE32VWLE@SOIC28 [CX1033]  
MC9S08QE32VWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE4CLC@QFP32 [CX3001]  
MC9S08QE4CLC@QFP32(auto trim) [CX3001]  
MC9S08QE4CLCE@QFP32 [CX3001]  
MC9S08QE4CLCE@QFP32(auto trim) [CX3001]  
MC9S08QE4CPG MC9S08QE4CPG(auto trim)  
MC9S08QE4CPGE MC9S08QE4CPGE(auto trim)  
MC9S08QE4CTG@TSSOP16 [CX1000]

MC9S08QE4CTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE4CTGE@TSSOP16 [CX1000]  
MC9S08QE4CTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE4CWJ@SOIC20 [CX1033]  
MC9S08QE4CWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE4CWJE@SOIC20 [CX1033]  
MC9S08QE4CWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE4CWL@SOIC28 [CX1033]  
MC9S08QE4CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE4CWLE@SOIC28 [CX1033]  
MC9S08QE4CWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE4MLC@QFP32 [CX3001]  
MC9S08QE4MLC@QFP32(auto trim) [CX3001]  
MC9S08QE4MLCE@QFP32 [CX3001]  
MC9S08QE4MLCE@QFP32(auto trim) [CX3001]  
MC9S08QE4MPG MC9S08QE4MPG(auto trim)  
MC9S08QE4MPGE MC9S08QE4MPGE(auto trim)  
MC9S08QE4MTG@TSSOP16 [CX1000]  
MC9S08QE4MTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE4MTGE@TSSOP16 [CX1000]  
MC9S08QE4MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE4MWJ@SOIC20 [CX1033]  
MC9S08QE4MWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE4MWJE@SOIC20 [CX1033]  
MC9S08QE4MWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE4MWL@SOIC28 [CX1033]  
MC9S08QE4MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE4MWLE@SOIC28 [CX1033]  
MC9S08QE4MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE4VLC@QFP32 [CX3001]  
MC9S08QE4VLC@QFP32(auto trim) [CX3001]  
MC9S08QE4VLC@QFP32 [CX3001]  
MC9S08QE4VLC@QFP32(auto trim) [CX3001]  
MC9S08QE4VPG MC9S08QE4VPG(auto trim)  
MC9S08QE4VPGE MC9S08QE4VPGE(auto trim)  
MC9S08QE4VTG@TSSOP16 [CX1000]  
MC9S08QE4VTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE4VTGE@TSSOP16 [CX1000]  
MC9S08QE4VTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE4VWJ@SOIC20 [CX1033]  
MC9S08QE4VWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE4VWJE@SOIC20 [CX1033]  
MC9S08QE4VWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE4VWL@SOIC28 [CX1033]  
MC9S08QE4VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE4VWLE@SOIC28 [CX1033]  
MC9S08QE4VWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE64CFT@QFN48 [CX4021] MC9S08QE64CFTE@QFN48 [CX4021]  
MC9S08QE64CLC@QFP32 [CX3001] MC9S08QE64CLCE@QFP32 [CX3001]  
MC9S08QE64CLD@QFP44 [CX3005] MC9S08QE64CLDE@QFP44 [CX3005]  
MC9S08QE64CLH@QFP64 [CX3011] MC9S08QE64CLHE@QFP64 [CX3011]  
MC9S08QE64CLK@QFP80 [CX3017] MC9S08QE64CLKE@QFP80 [CX3017]  
MC9S08QE64MFT@QFN48 [CX4021] MC9S08QE64MFTE@QFN48 [CX4021]  
MC9S08QE64MLC@QFP32 [CX3001] MC9S08QE64MLCE@QFP32 [CX3001]  
MC9S08QE64MLD@QFP44 [CX3005] MC9S08QE64MLDE@QFP44 [CX3005]  
MC9S08QE64MLH@QFP64 [CX3011] MC9S08QE64MLHE@QFP64 [CX3011]  
MC9S08QE64MLK@QFP80 [CX3017] MC9S08QE64MLKE@QFP80 [CX3017]  
MC9S08QE64VFT@QFN48 [CX4021] MC9S08QE64VFTE@QFN48 [CX4021]  
MC9S08QE64VLC@QFP32 [CX3001] MC9S08QE64VLC@QFP32 [CX3001]

MC9S08QE64VLD@QFP44 [CX3005]                    MC9S08QE64VLDE@QFP44 [CX3005]  
MC9S08QE64VLH@QFP64 [CX3011]                   MC9S08QE64VLHE@QFP64 [CX3011]  
MC9S08QE64VLK@QFP80 [CX3017]                   MC9S08QE64VLKE@QFP80 [CX3017]  
MC9S08QE8CLC@QFP32 [CX3001]  
MC9S08QE8CLC@QFP32(auto trim) [CX3001]  
MC9S08QE8CLCE@QFP32 [CX3001]  
MC9S08QE8CLCE@QFP32(auto trim) [CX3001]  
MC9S08QE8CPG                                    MC9S08QE8CPG(auto trim)  
MC9S08QE8CPGE                                   MC9S08QE8CPGE(auto trim)  
MC9S08QE8CTG@TSSOP16 [CX1000]  
MC9S08QE8CTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE8CTGE@TSSOP16 [CX1000]  
MC9S08QE8CTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE8CWJ@SOIC20 [CX1033]  
MC9S08QE8CWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE8CWJE@SOIC20 [CX1033]  
MC9S08QE8CWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE8CWL@SOIC28 [CX1033]  
MC9S08QE8CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE8CWLE@SOIC28 [CX1033]  
MC9S08QE8CWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE8MLC@QFP32 [CX3001]  
MC9S08QE8MLC@QFP32(auto trim) [CX3001]  
MC9S08QE8MLCE@QFP32 [CX3001]  
MC9S08QE8MLCE@QFP32(auto trim) [CX3001]  
MC9S08QE8MPG                                   MC9S08QE8MPG(auto trim)  
MC9S08QE8MPGE                                   MC9S08QE8MPGE(auto trim)  
MC9S08QE8MTG@TSSOP16 [CX1000]  
MC9S08QE8MTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE8MTGE@TSSOP16 [CX1000]  
MC9S08QE8MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE8MWJ@SOIC20 [CX1033]  
MC9S08QE8MWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE8MWJE@SOIC20 [CX1033]  
MC9S08QE8MWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE8MWL@SOIC28 [CX1033]  
MC9S08QE8MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE8MWLE@SOIC28 [CX1033]  
MC9S08QE8MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE8VLC@QFP32 [CX3001]  
MC9S08QE8VLC@QFP32(auto trim) [CX3001]  
MC9S08QE8VLC@QFP32 [CX3001]  
MC9S08QE8VLC@QFP32(auto trim) [CX3001]  
MC9S08QE8VPG                                   MC9S08QE8VPG(auto trim)  
MC9S08QE8VPGE                                   MC9S08QE8VPGE(auto trim)  
MC9S08QE8VTG@TSSOP16 [CX1000]  
MC9S08QE8VTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE8VTGE@TSSOP16 [CX1000]  
MC9S08QE8VTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE8VWJ@SOIC20 [CX1033]  
MC9S08QE8VWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE8VWJE@SOIC20 [CX1033]  
MC9S08QE8VWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE8VWL@SOIC28 [CX1033]  
MC9S08QE8VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE8VWLE@SOIC28 [CX1033]  
MC9S08QE8VWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE96CFT@QFN48 [CX4021]                   MC9S08QE96CFTE@QFN48 [CX4021]  
MC9S08QE96CLC@QFP32 [CX3001]                   MC9S08QE96CLCE@QFP32 [CX3001]

MC9S08QE96CLD@QFP44 [CX3005]  
MC9S08QE96CLH@QFP64 [CX3011]  
MC9S08QE96CLK@QFP80 [CX3017]  
MC9S08QE96MFT@QFN48 [CX4021]  
MC9S08QE96MLC@QFP32 [CX3001]  
MC9S08QE96MLD@QFP44 [CX3005]  
MC9S08QE96MLH@QFP64 [CX3011]  
MC9S08QE96MLK@QFP80 [CX3017]  
MC9S08QE96VFT@QFN48 [CX4021]  
MC9S08QE96VLC@QFP32 [CX3001]  
MC9S08QE96VLD@QFP44 [CX3005]  
MC9S08QE96VLH@QFP64 [CX3011]  
MC9S08QE96VLK@QFP80 [CX3017]  
MC9S08QG4CDN@SOIC8 [CX1030]  
MC9S08QG4CDT@TSSOP16 [CX1000]  
MC9S08QG4CFF@QFN16 [CX4009]  
MC9S08QG4CFQ@DFN8 [CX4004]  
MC9S08QG4CPA  
MC9S08QG4MDN@SOIC8 [CX1030]  
MC9S08QG4MDT@TSSOP16 [CX1000]  
MC9S08QG4MFF@QFN16 [CX4009]  
MC9S08QG4MFQ@DFN8 [CX4004]  
MC9S08QG4MPA  
MC9S08QG4VDN@SOIC8 [CX1030]  
MC9S08QG4VDT@TSSOP16 [CX1000]  
MC9S08QG4VFF@QFN16 [CX4009]  
MC9S08QG4VFQ@DFN8 [CX4004]  
MC9S08QG4VPA  
MC9S08QG8CDN@SOIC8 [CX1030]  
MC9S08QG8CDT@TSSOP16 [CX1000]  
MC9S08QG8CFF@QFN16 [CX4009]  
MC9S08QG8CFQ@DFN8 [CX4004]  
MC9S08QG8CPB  
MC9S08QG8MDN@SOIC8 [CX1030]  
MC9S08QG8MDT@TSSOP16 [CX1000]  
MC9S08QG8MFF@QFN16 [CX4009]  
MC9S08QG8MFQ@DFN8 [CX4004]  
MC9S08QG8MPB  
MC9S08QG8VDN@SOIC8 [CX1030]  
MC9S08QG8VDT@TSSOP16 [CX1000]  
MC9S08QG8VFF@QFN16 [CX4009]  
MC9S08QG8VFQ@DFN8 [CX4004]  
MC9S08QG8VPB  
MC9S08RC16CDW@SOIC28 [CX1033]  
MC9S08RC16CFD@QFN48 [CX4021]  
MC9S08RC16CFG@LQFP44 [CX3003]  
MC9S08RC16CFJ@LQFP32 [CX3001]  
MC9S08RC16CP  
MC9S08RC16MDW@SOIC28 [CX1033]  
MC9S08RC16MFD@QFN48 [CX4021]  
MC9S08RC16MFG@LQFP44 [CX3003]  
MC9S08RC16MFJ@LQFP32 [CX3001]  
MC9S08RC16MP  
MC9S08RC16VDW@SOIC28 [CX1033]  
MC9S08RC16VFD@QFN48 [CX4021]  
MC9S08RC16VFG@LQFP44 [CX3003]  
MC9S08RC16VFJ@LQFP32 [CX3001]  
MC9S08RC16VP  
MC9S08RC32CDW@SOIC28 [CX1033]

MC9S08QE96CLDE@QFP44 [CX3005]  
MC9S08QE96CLHE@QFP64 [CX3011]  
MC9S08QE96CLKE@QFP80 [CX3017]  
MC9S08QE96MFTE@QFN48 [CX4021]  
MC9S08QE96MLCE@QFP32 [CX3001]  
MC9S08QE96MLDE@QFP44 [CX3005]  
MC9S08QE96MLHE@QFP64 [CX3011]  
MC9S08QE96MLKE@QFP80 [CX3017]  
MC9S08QE96VFTE@QFN48 [CX4021]  
MC9S08QE96VLC@QFP32 [CX3001]  
MC9S08QE96VLDE@QFP44 [CX3005]  
MC9S08QE96VLHE@QFP64 [CX3011]  
MC9S08QE96VLKE@QFP80 [CX3017]  
MC9S08QG4CDNE@SOIC8 [CX1030]  
MC9S08QG4CDTE@TSSOP16 [CX1000]  
MC9S08QG4CFFE@QFN16 [CX4009]  
MC9S08QG4CFQE@DFN8 [CX4004]  
MC9S08QG4CPAE  
MC9S08QG4MDNE@SOIC8 [CX1030]  
MC9S08QG4MDTE@TSSOP16 [CX1000]  
MC9S08QG4MFFE@QFN16 [CX4009]  
MC9S08QG4MFQE@DFN8 [CX4004]  
MC9S08QG4MPAE  
MC9S08QG4VDNE@SOIC8 [CX1030]  
MC9S08QG4VDTE@TSSOP16 [CX1000]  
MC9S08QG4VFFE@QFN16 [CX4009]  
MC9S08QG4VFQE@DFN8 [CX4004]  
MC9S08QG4VPAE  
MC9S08QG8CDNE@SOIC8 [CX1030]  
MC9S08QG8CDTE@TSSOP16 [CX1000]  
MC9S08QG8CFFE@QFN16 [CX4009]  
MC9S08QG8CFQE@DFN8 [CX4004]  
MC9S08QG8CPBE  
MC9S08QG8MDNE@SOIC8 [CX1030]  
MC9S08QG8MDTE@TSSOP16 [CX1000]  
MC9S08QG8MFFE@QFN16 [CX4009]  
MC9S08QG8MFQE@DFN8 [CX4004]  
MC9S08QG8MPBE  
MC9S08QG8VDNE@SOIC8 [CX1030]  
MC9S08QG8VDTE@TSSOP16 [CX1000]  
MC9S08QG8VFFE@QFN16 [CX4009]  
MC9S08QG8VFQE@DFN8 [CX4004]  
MC9S08QG8VPBE  
MC9S08RC16CDWE@SOIC28 [CX1033]  
MC9S08RC16CFDE@QFN48 [CX4021]  
MC9S08RC16CFGE@LQFP44 [CX3003]  
MC9S08RC16CFJE@LQFP32 [CX3001]  
MC9S08RC16CPE  
MC9S08RC16MDWE@SOIC28 [CX1033]  
MC9S08RC16MFDE@QFN48 [CX4021]  
MC9S08RC16MFG@LQFP44 [CX3003]  
MC9S08RC16MFJE@LQFP32 [CX3001]  
MC9S08RC16MPE  
MC9S08RC16VDWE@SOIC28 [CX1033]  
MC9S08RC16VFDE@QFN48 [CX4021]  
MC9S08RC16VFG@LQFP44 [CX3003]  
MC9S08RC16VFJE@LQFP32 [CX3001]  
MC9S08RC16VPE  
MC9S08RC32CDWE@SOIC28 [CX1033]

MC9S08RC32CFD@QFN48 [CX4021]  
MC9S08RC32CFG@LQFP44 [CX3003]  
MC9S08RC32CFJ@LQFP32 [CX3001]  
MC9S08RC32CP  
MC9S08RC32MDW@SOIC28 [CX1033]  
MC9S08RC32MFD@QFN48 [CX4021]  
MC9S08RC32MFG@LQFP44 [CX3003]  
MC9S08RC32MFJ@LQFP32 [CX3001]  
MC9S08RC32MP  
MC9S08RC32VDW@SOIC28 [CX1033]  
MC9S08RC32VFD@QFN48 [CX4021]  
MC9S08RC32VFG@LQFP44 [CX3003]  
MC9S08RC32VFJ@LQFP32 [CX3001]  
MC9S08RC32VP  
MC9S08RC60CDW@SOIC28 [CX1033]  
MC9S08RC60CFD@QFN48 [CX4021]  
MC9S08RC60CFG@LQFP44 [CX3003]  
MC9S08RC60CFJ@LQFP32 [CX3001]  
MC9S08RC60CP  
MC9S08RC60MDW@SOIC28 [CX1033]  
MC9S08RC60MFD@QFN48 [CX4021]  
MC9S08RC60MFG@LQFP44 [CX3003]  
MC9S08RC60MFJ@LQFP32 [CX3001]  
MC9S08RC60MP  
MC9S08RC60VDW@SOIC28 [CX1033]  
MC9S08RC60VFD@QFN48 [CX4021]  
MC9S08RC60VFG@LQFP44 [CX3003]  
MC9S08RC60VFJ@LQFP32 [CX3001]  
MC9S08RC60VP  
MC9S08RC8CDW@SOIC28 [CX1033]  
MC9S08RC8CFD@QFN48 [CX4021]  
MC9S08RC8CFG@LQFP44 [CX3003]  
MC9S08RC8CFJ@LQFP32 [CX3001]  
MC9S08RC8CP  
MC9S08RC8MDW@SOIC28 [CX1033]  
MC9S08RC8MFD@QFN48 [CX4021]  
MC9S08RC8MFG@LQFP44 [CX3003]  
MC9S08RC8MFJ@LQFP32 [CX3001]  
MC9S08RC8MP  
MC9S08RC8VDW@SOIC28 [CX1033]  
MC9S08RC8VFD@QFN48 [CX4021]  
MC9S08RC8VFG@LQFP44 [CX3003]  
MC9S08RC8VFJ@LQFP32 [CX3001]  
MC9S08RC8VP  
MC9S08RD16CDW@SOIC28 [CX1033]  
MC9S08RD16CFD@QFN48 [CX4021]  
MC9S08RD16CFG@LQFP44 [CX3003]  
MC9S08RD16CFJ@LQFP32 [CX3001]  
MC9S08RD16CP  
MC9S08RD16MDW@SOIC28 [CX1033]  
MC9S08RD16MFD@QFN48 [CX4021]  
MC9S08RD16MFG@LQFP44 [CX3003]  
MC9S08RD16MFJ@LQFP32 [CX3001]  
MC9S08RD16MP  
MC9S08RD16VDW@SOIC28 [CX1033]  
MC9S08RD16VFD@QFN48 [CX4021]  
MC9S08RD16VFG@LQFP44 [CX3003]  
MC9S08RD16VFJ@LQFP32 [CX3001]  
MC9S08RD16VP

MC9S08RC32CFDE@QFN48 [CX4021]  
MC9S08RC32CFGE@LQFP44 [CX3003]  
MC9S08RC32CFJE@LQFP32 [CX3001]  
MC9S08RC32CPE  
MC9S08RC32MDWE@SOIC28 [CX1033]  
MC9S08RC32MFDE@QFN48 [CX4021]  
MC9S08RC32MFGE@LQFP44 [CX3003]  
MC9S08RC32MFJE@LQFP32 [CX3001]  
MC9S08RC32MPE  
MC9S08RC32VDWE@SOIC28 [CX1033]  
MC9S08RC32VFDE@QFN48 [CX4021]  
MC9S08RC32VFGE@LQFP44 [CX3003]  
MC9S08RC32VFJE@LQFP32 [CX3001]  
MC9S08RC32VPE  
MC9S08RC60CDWE@SOIC28 [CX1033]  
MC9S08RC60CFDE@QFN48 [CX4021]  
MC9S08RC60CFGE@LQFP44 [CX3003]  
MC9S08RC60CFJE@LQFP32 [CX3001]  
MC9S08RC60CPE  
MC9S08RC60MDWE@SOIC28 [CX1033]  
MC9S08RC60MFDE@QFN48 [CX4021]  
MC9S08RC60MFGE@LQFP44 [CX3003]  
MC9S08RC60MFJE@LQFP32 [CX3001]  
MC9S08RC60MPE  
MC9S08RC60VDWE@SOIC28 [CX1033]  
MC9S08RC60VFDE@QFN48 [CX4021]  
MC9S08RC60VFGE@LQFP44 [CX3003]  
MC9S08RC60VFJE@LQFP32 [CX3001]  
MC9S08RC60VPE  
MC9S08RC8CDWE@SOIC28 [CX1033]  
MC9S08RC8CFDE@QFN48 [CX4021]  
MC9S08RC8CFGE@LQFP44 [CX3003]  
MC9S08RC8CFJE@LQFP32 [CX3001]  
MC9S08RC8CPE  
MC9S08RC8MDWE@SOIC28 [CX1033]  
MC9S08RC8MFDE@QFN48 [CX4021]  
MC9S08RC8MFGE@LQFP44 [CX3003]  
MC9S08RC8MFJE@LQFP32 [CX3001]  
MC9S08RC8MPE  
MC9S08RC8VDWE@SOIC28 [CX1033]  
MC9S08RC8VFDE@QFN48 [CX4021]  
MC9S08RC8VFGE@LQFP44 [CX3003]  
MC9S08RC8VFJE@LQFP32 [CX3001]  
MC9S08RC8VPE  
MC9S08RD16CDWE@SOIC28 [CX1033]  
MC9S08RD16CFDE@QFN48 [CX4021]  
MC9S08RD16CFGE@LQFP44 [CX3003]  
MC9S08RD16CFJE@LQFP32 [CX3001]  
MC9S08RD16CPE  
MC9S08RD16MDWE@SOIC28 [CX1033]  
MC9S08RD16MFDE@QFN48 [CX4021]  
MC9S08RD16MFGE@LQFP44 [CX3003]  
MC9S08RD16MFJE@LQFP32 [CX3001]  
MC9S08RD16MPE  
MC9S08RD16VDWE@SOIC28 [CX1033]  
MC9S08RD16VFDE@QFN48 [CX4021]  
MC9S08RD16VFGE@LQFP44 [CX3003]  
MC9S08RD16VFJE@LQFP32 [CX3001]  
MC9S08RD16VPE

MC9S08RD32CDW@SOIC28 [CX1033]  
MC9S08RD32CFD@QFN48 [CX4021]  
MC9S08RD32CFG@LQFP44 [CX3003]  
MC9S08RD32CFJ@LQFP32 [CX3001]  
MC9S08RD32CP  
MC9S08RD32MDW@SOIC28 [CX1033]  
MC9S08RD32MFD@QFN48 [CX4021]  
MC9S08RD32MFG@LQFP44 [CX3003]  
MC9S08RD32MFJ@LQFP32 [CX3001]  
MC9S08RD32MP  
MC9S08RD32VDW@SOIC28 [CX1033]  
MC9S08RD32VFD@QFN48 [CX4021]  
MC9S08RD32VFG@LQFP44 [CX3003]  
MC9S08RD32VFJ@LQFP32 [CX3001]  
MC9S08RD32VP  
MC9S08RD60CDW@SOIC28 [CX1033]  
MC9S08RD60CFD@QFN48 [CX4021]  
MC9S08RD60CFG@LQFP44 [CX3003]  
MC9S08RD60CFJ@LQFP32 [CX3001]  
MC9S08RD60CP  
MC9S08RD60MDW@SOIC28 [CX1033]  
MC9S08RD60MFD@QFN48 [CX4021]  
MC9S08RD60MFG@LQFP44 [CX3003]  
MC9S08RD60MFJ@LQFP32 [CX3001]  
MC9S08RD60MP  
MC9S08RD60VDW@SOIC28 [CX1033]  
MC9S08RD60VFD@QFN48 [CX4021]  
MC9S08RD60VFG@LQFP44 [CX3003]  
MC9S08RD60VFJ@LQFP32 [CX3001]  
MC9S08RD60VP  
MC9S08RD8CDW@SOIC28 [CX1033]  
MC9S08RD8CFD@QFN48 [CX4021]  
MC9S08RD8CFG@LQFP44 [CX3003]  
MC9S08RD8CFJ@LQFP32 [CX3001]  
MC9S08RD8CP  
MC9S08RD8MDW@SOIC28 [CX1033]  
MC9S08RD8MFD@QFN48 [CX4021]  
MC9S08RD8MFG@LQFP44 [CX3003]  
MC9S08RD8MFJ@LQFP32 [CX3001]  
MC9S08RD8MP  
MC9S08RD8VDW@SOIC28 [CX1033]  
MC9S08RD8VFD@QFN48 [CX4021]  
MC9S08RD8VFG@LQFP44 [CX3003]  
MC9S08RD8VFJ@LQFP32 [CX3001]  
MC9S08RD8VP  
MC9S08RE16CDW@SOIC28 [CX1033]  
MC9S08RE16CFD@QFN48 [CX4021]  
MC9S08RE16CFG@LQFP44 [CX3003]  
MC9S08RE16CFJ@LQFP32 [CX3001]  
MC9S08RE16CP  
MC9S08RE16MDW@SOIC28 [CX1033]  
MC9S08RE16MFD@QFN48 [CX4021]  
MC9S08RE16MFG@LQFP44 [CX3003]  
MC9S08RE16MFJ@LQFP32 [CX3001]  
MC9S08RE16MP  
MC9S08RE16VDW@SOIC28 [CX1033]  
MC9S08RE16VFD@QFN48 [CX4021]  
MC9S08RE16VFG@LQFP44 [CX3003]  
MC9S08RE16VFJ@LQFP32 [CX3001]

MC9S08RD32CDWE@SOIC28 [CX1033]  
MC9S08RD32CFDE@QFN48 [CX4021]  
MC9S08RD32CFGE@LQFP44 [CX3003]  
MC9S08RD32CFJE@LQFP32 [CX3001]  
MC9S08RD32CPE  
MC9S08RD32MDWE@SOIC28 [CX1033]  
MC9S08RD32MFDE@QFN48 [CX4021]  
MC9S08RD32MFGE@LQFP44 [CX3003]  
MC9S08RD32MFJE@LQFP32 [CX3001]  
MC9S08RD32MPE  
MC9S08RD32VDWE@SOIC28 [CX1033]  
MC9S08RD32VFDE@QFN48 [CX4021]  
MC9S08RD32VFGE@LQFP44 [CX3003]  
MC9S08RD32VFJE@LQFP32 [CX3001]  
MC9S08RD32VPE  
MC9S08RD60CDWE@SOIC28 [CX1033]  
MC9S08RD60CFDE@QFN48 [CX4021]  
MC9S08RD60CFGE@LQFP44 [CX3003]  
MC9S08RD60CFJE@LQFP32 [CX3001]  
MC9S08RD60CPE  
MC9S08RD60MDWE@SOIC28 [CX1033]  
MC9S08RD60MFDE@QFN48 [CX4021]  
MC9S08RD60MFGE@LQFP44 [CX3003]  
MC9S08RD60MFJE@LQFP32 [CX3001]  
MC9S08RD60MPE  
MC9S08RD60VDWE@SOIC28 [CX1033]  
MC9S08RD60VFDE@QFN48 [CX4021]  
MC9S08RD60VFGE@LQFP44 [CX3003]  
MC9S08RD60VFJE@LQFP32 [CX3001]  
MC9S08RD60VPE  
MC9S08RD8CDWE@SOIC28 [CX1033]  
MC9S08RD8CFDE@QFN48 [CX4021]  
MC9S08RD8CFGE@LQFP44 [CX3003]  
MC9S08RD8CFJE@LQFP32 [CX3001]  
MC9S08RD8CPE  
MC9S08RD8MDWE@SOIC28 [CX1033]  
MC9S08RD8MFDE@QFN48 [CX4021]  
MC9S08RD8MFGE@LQFP44 [CX3003]  
MC9S08RD8MFJE@LQFP32 [CX3001]  
MC9S08RD8MPE  
MC9S08RD8VDWE@SOIC28 [CX1033]  
MC9S08RD8VFDE@QFN48 [CX4021]  
MC9S08RD8VFGE@LQFP44 [CX3003]  
MC9S08RD8VFJE@LQFP32 [CX3001]  
MC9S08RD8VPE  
MC9S08RE16CDWE@SOIC28 [CX1033]  
MC9S08RE16CFDE@QFN48 [CX4021]  
MC9S08RE16CFGE@LQFP44 [CX3003]  
MC9S08RE16CFJE@LQFP32 [CX3001]  
MC9S08RE16CPE  
MC9S08RE16MDWE@SOIC28 [CX1033]  
MC9S08RE16MFDE@QFN48 [CX4021]  
MC9S08RE16MFGE@LQFP44 [CX3003]  
MC9S08RE16MFJE@LQFP32 [CX3001]  
MC9S08RE16MPE  
MC9S08RE16VDWE@SOIC28 [CX1033]  
MC9S08RE16VFDE@QFN48 [CX4021]  
MC9S08RE16VFGE@LQFP44 [CX3003]  
MC9S08RE16VFJE@LQFP32 [CX3001]



MC9S08RE16VP  
MC9S08RE32CDW@SOIC28 [CX1033]  
MC9S08RE32CFD@QFN48 [CX4021]  
MC9S08RE32CFG@LQFP44 [CX3003]  
MC9S08RE32CFJ@LQFP32 [CX3001]  
MC9S08RE32CP  
MC9S08RE32MDW@SOIC28 [CX1033]  
MC9S08RE32MFD@QFN48 [CX4021]  
MC9S08RE32MFG@LQFP44 [CX3003]  
MC9S08RE32MFJ@LQFP32 [CX3001]  
MC9S08RE32MP  
MC9S08RE32VDW@SOIC28 [CX1033]  
MC9S08RE32VFD@QFN48 [CX4021]  
MC9S08RE32VFG@LQFP44 [CX3003]  
MC9S08RE32VFJ@LQFP32 [CX3001]  
MC9S08RE32VP  
MC9S08RE60CDW@SOIC28 [CX1033]  
MC9S08RE60CFD@QFN48 [CX4021]  
MC9S08RE60CFG@LQFP44 [CX3003]  
MC9S08RE60CFJ@LQFP32 [CX3001]  
MC9S08RE60CP  
MC9S08RE60MDW@SOIC28 [CX1033]  
MC9S08RE60MFD@QFN48 [CX4021]  
MC9S08RE60MFG@LQFP44 [CX3003]  
MC9S08RE60MFJ@LQFP32 [CX3001]  
MC9S08RE60MP  
MC9S08RE60VDW@SOIC28 [CX1033]  
MC9S08RE60VFD@QFN48 [CX4021]  
MC9S08RE60VFG@LQFP44 [CX3003]  
MC9S08RE60VFJ@LQFP32 [CX3001]  
MC9S08RE60VP  
MC9S08RE8CDW@SOIC28 [CX1033]  
MC9S08RE8CFD@QFN48 [CX4021]  
MC9S08RE8CFG@LQFP44 [CX3003]  
MC9S08RE8CFJ@LQFP32 [CX3001]  
MC9S08RE8CP  
MC9S08RE8MDW@SOIC28 [CX1033]  
MC9S08RE8MFD@QFN48 [CX4021]  
MC9S08RE8MFG@LQFP44 [CX3003]  
MC9S08RE8MFJ@LQFP32 [CX3001]  
MC9S08RE8MP  
MC9S08RE8VDW@SOIC28 [CX1033]  
MC9S08RE8VFD@QFN48 [CX4021]  
MC9S08RE8VFG@LQFP44 [CX3003]  
MC9S08RE8VFJ@LQFP32 [CX3001]  
MC9S08RE8VP  
MC9S08RG16CDW@SOIC28 [CX1033]  
MC9S08RG16CFD@QFN48 [CX4021]  
MC9S08RG16CFG@LQFP44 [CX3003]  
MC9S08RG16CFJ@LQFP32 [CX3001]  
MC9S08RG16CP  
MC9S08RG16MDW@SOIC28 [CX1033]  
MC9S08RG16MFD@QFN48 [CX4021]  
MC9S08RG16MFG@LQFP44 [CX3003]  
MC9S08RG16MFJ@LQFP32 [CX3001]  
MC9S08RG16MP  
MC9S08RG16VDW@SOIC28 [CX1033]  
MC9S08RG16VFD@QFN48 [CX4021]  
MC9S08RG16VFG@LQFP44 [CX3003]

MC9S08RE16VPE  
MC9S08RE32CDWE@SOIC28 [CX1033]  
MC9S08RE32CFDE@QFN48 [CX4021]  
MC9S08RE32CFGE@LQFP44 [CX3003]  
MC9S08RE32CFJE@LQFP32 [CX3001]  
MC9S08RE32CPE  
MC9S08RE32MDWE@SOIC28 [CX1033]  
MC9S08RE32MFDE@QFN48 [CX4021]  
MC9S08RE32MFGE@LQFP44 [CX3003]  
MC9S08RE32MFJE@LQFP32 [CX3001]  
MC9S08RE32MPE  
MC9S08RE32VDWE@SOIC28 [CX1033]  
MC9S08RE32VFDE@QFN48 [CX4021]  
MC9S08RE32VFGE@LQFP44 [CX3003]  
MC9S08RE32VFJE@LQFP32 [CX3001]  
MC9S08RE32VPE  
MC9S08RE60CDWE@SOIC28 [CX1033]  
MC9S08RE60CFDE@QFN48 [CX4021]  
MC9S08RE60CFGE@LQFP44 [CX3003]  
MC9S08RE60CFJE@LQFP32 [CX3001]  
MC9S08RE60CPE  
MC9S08RE60MDWE@SOIC28 [CX1033]  
MC9S08RE60MFDE@QFN48 [CX4021]  
MC9S08RE60MFGE@LQFP44 [CX3003]  
MC9S08RE60MFJE@LQFP32 [CX3001]  
MC9S08RE60MPE  
MC9S08RE60VDWE@SOIC28 [CX1033]  
MC9S08RE60VFDE@QFN48 [CX4021]  
MC9S08RE60VFGE@LQFP44 [CX3003]  
MC9S08RE60VFJE@LQFP32 [CX3001]  
MC9S08RE60VPE  
MC9S08RE8CDWE@SOIC28 [CX1033]  
MC9S08RE8CFDE@QFN48 [CX4021]  
MC9S08RE8CFGE@LQFP44 [CX3003]  
MC9S08RE8CFJE@LQFP32 [CX3001]  
MC9S08RE8CPE  
MC9S08RE8MDWE@SOIC28 [CX1033]  
MC9S08RE8MFDE@QFN48 [CX4021]  
MC9S08RE8MFGE@LQFP44 [CX3003]  
MC9S08RE8MFJE@LQFP32 [CX3001]  
MC9S08RE8MPE  
MC9S08RE8VDWE@SOIC28 [CX1033]  
MC9S08RE8VFDE@QFN48 [CX4021]  
MC9S08RE8VFGE@LQFP44 [CX3003]  
MC9S08RE8VFJE@LQFP32 [CX3001]  
MC9S08RE8VPE  
MC9S08RG16CDWE@SOIC28 [CX1033]  
MC9S08RG16CFDE@QFN48 [CX4021]  
MC9S08RG16CFGE@LQFP44 [CX3003]  
MC9S08RG16CFJE@LQFP32 [CX3001]  
MC9S08RG16CPE  
MC9S08RG16MDWE@SOIC28 [CX1033]  
MC9S08RG16MFDE@QFN48 [CX4021]  
MC9S08RG16MFGE@LQFP44 [CX3003]  
MC9S08RG16MFJE@LQFP32 [CX3001]  
MC9S08RG16MPE  
MC9S08RG16VDWE@SOIC28 [CX1033]  
MC9S08RG16VFDE@QFN48 [CX4021]  
MC9S08RG16VFGE@LQFP44 [CX3003]

MC9S08RG16VFJ@LQFP32 [CX3001]  
MC9S08RG16VP  
MC9S08RG32CDW@SOIC28 [CX1033]  
MC9S08RG32CFD@QFN48 [CX4021]  
MC9S08RG32CFG@LQFP44 [CX3003]  
MC9S08RG32CFJ@LQFP32 [CX3001]  
MC9S08RG32CP  
MC9S08RG32MDW@SOIC28 [CX1033]  
MC9S08RG32MFD@QFN48 [CX4021]  
MC9S08RG32MFG@LQFP44 [CX3003]  
MC9S08RG32MFJ@LQFP32 [CX3001]  
MC9S08RG32MP  
MC9S08RG32VDW@SOIC28 [CX1033]  
MC9S08RG32VFD@QFN48 [CX4021]  
MC9S08RG32VFG@LQFP44 [CX3003]  
MC9S08RG32VFJ@LQFP32 [CX3001]  
MC9S08RG32VP  
MC9S08RG60CDW@SOIC28 [CX1033]  
MC9S08RG60CFD@QFN48 [CX4021]  
MC9S08RG60CFG@LQFP44 [CX3003]  
MC9S08RG60CFJ@LQFP32 [CX3001]  
MC9S08RG60CP  
MC9S08RG60MDW@SOIC28 [CX1033]  
MC9S08RG60MFD@QFN48 [CX4021]  
MC9S08RG60MFG@LQFP44 [CX3003]  
MC9S08RG60MFJ@LQFP32 [CX3001]  
MC9S08RG60MP  
MC9S08RG60VDW@SOIC28 [CX1033]  
MC9S08RG60VFD@QFN48 [CX4021]  
MC9S08RG60VFG@LQFP44 [CX3003]  
MC9S08RG60VFJ@LQFP32 [CX3001]  
MC9S08RG60VP  
MC9S08RG8CDW@SOIC28 [CX1033]  
MC9S08RG8CFD@QFN48 [CX4021]  
MC9S08RG8CFG@LQFP44 [CX3003]  
MC9S08RG8CFJ@LQFP32 [CX3001]  
MC9S08RG8CP  
MC9S08RG8MDW@SOIC28 [CX1033]  
MC9S08RG8MFD@QFN48 [CX4021]  
MC9S08RG8MFG@LQFP44 [CX3003]  
MC9S08RG8MFJ@LQFP32 [CX3001]  
MC9S08RG8MP  
MC9S08RG8VDW@SOIC28 [CX1033]  
MC9S08RG8VFD@QFN48 [CX4021]  
MC9S08RG8VFG@LQFP44 [CX3003]  
MC9S08RG8VFJ@LQFP32 [CX3001]  
MC9S08RG8VP  
MC9S08SE4CRL [CX0001]  
MC9S08SE4CWL [CX1033]  
MC9S08SE4MTG [CX1001]  
MC9S08SE4VRL [CX0001]  
MC9S08SE4VWL [CX1033]  
MC9S08SE8CTG [CX1001]  
MC9S08SE8MRL [CX0001]  
MC9S08SE8MWL [CX1033]  
MC9S08SE8VTG [CX1001]  
MC9S08SG16CTG@TSSOP16 [CX1000]  
MC9S08SG16CTJ@TSSOP20 [CX1000]  
MC9S08SG16CTL@TSSOP28 [CX1001]

MC9S08RG16VFJE@LQFP32 [CX3001]  
MC9S08RG16VPE  
MC9S08RG32CDWE@SOIC28 [CX1033]  
MC9S08RG32CFDE@QFN48 [CX4021]  
MC9S08RG32CFGE@LQFP44 [CX3003]  
MC9S08RG32CFJE@LQFP32 [CX3001]  
MC9S08RG32CPE  
MC9S08RG32MDWE@SOIC28 [CX1033]  
MC9S08RG32MFDE@QFN48 [CX4021]  
MC9S08RG32MFGE@LQFP44 [CX3003]  
MC9S08RG32MFJE@LQFP32 [CX3001]  
MC9S08RG32MPE  
MC9S08RG32VDWE@SOIC28 [CX1033]  
MC9S08RG32VFDE@QFN48 [CX4021]  
MC9S08RG32VFGE@LQFP44 [CX3003]  
MC9S08RG32VFJE@LQFP32 [CX3001]  
MC9S08RG32VPE  
MC9S08RG60CDWE@SOIC28 [CX1033]  
MC9S08RG60CFDE@QFN48 [CX4021]  
MC9S08RG60CFGE@LQFP44 [CX3003]  
MC9S08RG60CFJE@LQFP32 [CX3001]  
MC9S08RG60CPE  
MC9S08RG60MDWE@SOIC28 [CX1033]  
MC9S08RG60MFDE@QFN48 [CX4021]  
MC9S08RG60MFGE@LQFP44 [CX3003]  
MC9S08RG60MFJE@LQFP32 [CX3001]  
MC9S08RG60MPE  
MC9S08RG60VDWE@SOIC28 [CX1033]  
MC9S08RG60VFDE@QFN48 [CX4021]  
MC9S08RG60VFGE@LQFP44 [CX3003]  
MC9S08RG60VFJE@LQFP32 [CX3001]  
MC9S08RG60VPE  
MC9S08RG8CDWE@SOIC28 [CX1033]  
MC9S08RG8CFDE@QFN48 [CX4021]  
MC9S08RG8CFGE@LQFP44 [CX3003]  
MC9S08RG8CFJE@LQFP32 [CX3001]  
MC9S08RG8CPE  
MC9S08RG8MDWE@SOIC28 [CX1033]  
MC9S08RG8MFDE@QFN48 [CX4021]  
MC9S08RG8MFGE@LQFP44 [CX3003]  
MC9S08RG8MFJE@LQFP32 [CX3001]  
MC9S08RG8MPE  
MC9S08RG8VDWE@SOIC28 [CX1033]  
MC9S08RG8VFDE@QFN48 [CX4021]  
MC9S08RG8VFGE@LQFP44 [CX3003]  
MC9S08RG8VFJE@LQFP32 [CX3001]  
MC9S08RG8VPE  
MC9S08SE4CTG [CX1001]  
MC9S08SE4MRL [CX0001]  
MC9S08SE4MWL [CX1033]  
MC9S08SE4VTG [CX1001]  
MC9S08SE8CRL [CX0001]  
MC9S08SE8CWL [CX1033]  
MC9S08SE8MTG [CX1001]  
MC9S08SE8VRL [CX0001]  
MC9S08SE8VWL [CX1033]  
MC9S08SG16CTGE@TSSOP16 [CX1000]  
MC9S08SG16CTJE@TSSOP20 [CX1000]  
MC9S08SG16CTLE@TSSOP28 [CX1001]

MC9S08SG16MTG@TSSOP16 [CX1000]      MC9S08SG16MTGE@TSSOP16 [CX1000]  
MC9S08SG16MTJ@TSSOP20 [CX1000]      MC9S08SG16MTJE@TSSOP20 [CX1000]  
MC9S08SG16MTL@TSSOP28 [CX1001]      MC9S08SG16MTLE@TSSOP28 [CX1001]  
MC9S08SG16VTG@TSSOP16 [CX1000]      MC9S08SG16VTGE@TSSOP16 [CX1000]  
MC9S08SG16VTJ@TSSOP20 [CX1000]      MC9S08SG16VTJE@TSSOP20 [CX1000]  
MC9S08SG16VTL@TSSOP28 [CX1001]      MC9S08SG16VTLE@TSSOP28 [CX1001]  
MC9S08SG32CTG@TSSOP16 [CX1000]      MC9S08SG32CTGE@TSSOP16 [CX1000]  
MC9S08SG32CTJ@TSSOP20 [CX1000]      MC9S08SG32CTJE@TSSOP20 [CX1000]  
MC9S08SG32CTL@TSSOP28 [CX1001]      MC9S08SG32CTLE@TSSOP28 [CX1001]  
MC9S08SG32MTG@TSSOP16 [CX1000]      MC9S08SG32MTGE@TSSOP16 [CX1000]  
MC9S08SG32MTJ@TSSOP20 [CX1000]      MC9S08SG32MTJE@TSSOP20 [CX1000]  
MC9S08SG32MTL@TSSOP28 [CX1001]      MC9S08SG32MTLE@TSSOP28 [CX1001]  
MC9S08SG32VTG@TSSOP16 [CX1000]      MC9S08SG32VTGE@TSSOP16 [CX1000]  
MC9S08SG32VTJ@TSSOP20 [CX1000]      MC9S08SG32VTJE@TSSOP20 [CX1000]  
MC9S08SG32VTL@TSSOP28 [CX1001]      MC9S08SG32VTLE@TSSOP28 [CX1001]  
MC9S08SG4CSC@SOIC8 [CX1030]      MC9S08SG4CSCE@SOIC8 [CX1030]  
MC9S08SG4CTG@TSSOP16 [CX1000]      MC9S08SG4CTGE@TSSOP16 [CX1000]  
MC9S08SG4CTJ@TSSOP20 [CX1000]      MC9S08SG4CTJE@TSSOP20 [CX1000]  
MC9S08SG4MSC@SOIC8 [CX1030]      MC9S08SG4MSCE@SOIC8 [CX1030]  
MC9S08SG4MTG@TSSOP16 [CX1000]      MC9S08SG4MTGE@TSSOP16 [CX1000]  
MC9S08SG4MTJ@TSSOP20 [CX1000]      MC9S08SG4MTJE@TSSOP20 [CX1000]  
MC9S08SG4VSC@SOIC8 [CX1030]      MC9S08SG4VSCE@SOIC8 [CX1030]  
MC9S08SG4VTG@TSSOP16 [CX1000]      MC9S08SG4VTGE@TSSOP16 [CX1000]  
MC9S08SG4VTJ@TSSOP20 [CX1000]      MC9S08SG4VTJE@TSSOP20 [CX1000]  
MC9S08SG8CSC@SOIC8 [CX1030]      MC9S08SG8CSCE@SOIC8 [CX1030]  
MC9S08SG8CTG@TSSOP16 [CX1000]      MC9S08SG8CTGE@TSSOP16 [CX1000]  
MC9S08SG8CTJ@TSSOP20 [CX1000]      MC9S08SG8CTJE@TSSOP20 [CX1000]  
MC9S08SG8MSC@SOIC8 [CX1030]      MC9S08SG8MSCE@SOIC8 [CX1030]  
MC9S08SG8MTG@TSSOP16 [CX1000]      MC9S08SG8MTGE@TSSOP16 [CX1000]  
MC9S08SG8MTJ@TSSOP20 [CX1000]      MC9S08SG8MTJE@TSSOP20 [CX1000]  
MC9S08SG8VSC@SOIC8 [CX1030]      MC9S08SG8VSCE@SOIC8 [CX1030]  
MC9S08SG8VTG@TSSOP16 [CX1000]      MC9S08SG8VTGE@TSSOP16 [CX1000]  
MC9S08SG8VTJ@TSSOP20 [CX1000]      MC9S08SG8VTJE@TSSOP20 [CX1000]  
MC9S08SH16CTG@TSSOP16 [CX1000]      MC9S08SH16CTGE@TSSOP16 [CX1000]  
MC9S08SH16CTJ@TSSOP20 [CX1000]      MC9S08SH16CTJE@TSSOP20 [CX1000]  
MC9S08SH16CTL@TSSOP28 [CX1001]      MC9S08SH16CTLE@TSSOP28 [CX1001]  
MC9S08SH16CWL@SOIC28 [CX1033]      MC9S08SH16CWLE@SOIC28 [CX1033]  
MC9S08SH16MTG@TSSOP16 [CX1000]      MC9S08SH16MTGE@TSSOP16 [CX1000]  
MC9S08SH16MTJ@TSSOP20 [CX1000]      MC9S08SH16MTJE@TSSOP20 [CX1000]  
MC9S08SH16MTL@TSSOP28 [CX1001]      MC9S08SH16MTLE@TSSOP28 [CX1001]  
MC9S08SH16MWL@SOIC28 [CX1033]      MC9S08SH16MWLE@SOIC28 [CX1033]  
MC9S08SH16VTG@TSSOP16 [CX1000]      MC9S08SH16VTGE@TSSOP16 [CX1000]  
MC9S08SH16VTJ@TSSOP20 [CX1000]      MC9S08SH16VTJE@TSSOP20 [CX1000]  
MC9S08SH16VTL@TSSOP28 [CX1001]      MC9S08SH16VTLE@TSSOP28 [CX1001]  
MC9S08SH16VWL@SOIC28 [CX1033]      MC9S08SH16VWLE@SOIC28 [CX1033]  
MC9S08SH32CTG@TSSOP16 [CX1000]      MC9S08SH32CTGE@TSSOP16 [CX1000]  
MC9S08SH32CTJ@TSSOP20 [CX1000]      MC9S08SH32CTJE@TSSOP20 [CX1000]  
MC9S08SH32CTL@TSSOP28 [CX1001]      MC9S08SH32CTLE@TSSOP28 [CX1001]  
MC9S08SH32CWL@SOIC28 [CX1033]      MC9S08SH32CWLE@SOIC28 [CX1033]  
MC9S08SH32MTG@TSSOP16 [CX1000]      MC9S08SH32MTGE@TSSOP16 [CX1000]  
MC9S08SH32MTJ@TSSOP20 [CX1000]      MC9S08SH32MTJE@TSSOP20 [CX1000]  
MC9S08SH32MTL@TSSOP28 [CX1001]      MC9S08SH32MTLE@TSSOP28 [CX1001]  
MC9S08SH32MWL@SOIC28 [CX1033]      MC9S08SH32MWLE@SOIC28 [CX1033]  
MC9S08SH32VTG@TSSOP16 [CX1000]      MC9S08SH32VTGE@TSSOP16 [CX1000]  
MC9S08SH32VTJ@TSSOP20 [CX1000]      MC9S08SH32VTJE@TSSOP20 [CX1000]  
MC9S08SH32VTL@TSSOP28 [CX1001]      MC9S08SH32VTLE@TSSOP28 [CX1001]  
MC9S08SH32VWL@SOIC28 [CX1033]      MC9S08SH32VWLE@SOIC28 [CX1033]  
MC9S08SH4CFK@QFN24 [CX4012]  
MC9S08SH4CFK@QFN24(auto trim) [CX4012]

MC9S08SH4CFKE@QFN24 [CX4012]  
MC9S08SH4CFKE@QFN24(auto trim) [CX4012]  
MC9S08SH4CPJ MC9S08SH4CPJ(auto trim)  
MC9S08SH4CPJE MC9S08SH4CPJE(auto trim)  
MC9S08SH4CSC@SOIC8 [CX1030]  
MC9S08SH4CSC@SOIC8(auto trim) [CX1030]  
MC9S08SH4CSCE@SOIC8 [CX1030]  
MC9S08SH4CSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH4CTG@TSSOP16 [CX1000]  
MC9S08SH4CTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH4CTGE@TSSOP16 [CX1000]  
MC9S08SH4CTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH4CTJ@TSSOP20 [CX1000]  
MC9S08SH4CTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH4CTJE@TSSOP20 [CX1000]  
MC9S08SH4CTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH4CWJ@SOIC20 [CX1033]  
MC9S08SH4CWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH4CWJE@SOIC20 [CX1033]  
MC9S08SH4CWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH4MFK@QFN24 [CX4012]  
MC9S08SH4MFK@QFN24(auto trim) [CX4012]  
MC9S08SH4MFKE@QFN24 [CX4012]  
MC9S08SH4MFKE@QFN24(auto trim) [CX4012]  
MC9S08SH4MPJ MC9S08SH4MPJ(auto trim)  
MC9S08SH4MPJE MC9S08SH4MPJE(auto trim)  
MC9S08SH4MSC@SOIC8 [CX1030]  
MC9S08SH4MSC@SOIC8(auto trim) [CX1030]  
MC9S08SH4MSCE@SOIC8 [CX1030]  
MC9S08SH4MSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH4MTG@TSSOP16 [CX1000]  
MC9S08SH4MTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH4MTGE@TSSOP16 [CX1000]  
MC9S08SH4MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH4MTJ@TSSOP20 [CX1000]  
MC9S08SH4MTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH4MTJE@TSSOP20 [CX1000]  
MC9S08SH4MTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH4MWJ@SOIC20 [CX1033]  
MC9S08SH4MWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH4MWJE@SOIC20 [CX1033]  
MC9S08SH4MWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH4VFK@QFN24 [CX4012]  
MC9S08SH4VFK@QFN24(auto trim) [CX4012]  
MC9S08SH4VFKE@QFN24 [CX4012]  
MC9S08SH4VFKE@QFN24(auto trim) [CX4012]  
MC9S08SH4VPJ MC9S08SH4VPJ(auto trim)  
MC9S08SH4VPJE MC9S08SH4VPJE(auto trim)  
MC9S08SH4VSC@SOIC8 [CX1030]  
MC9S08SH4VSC@SOIC8(auto trim) [CX1030]  
MC9S08SH4VSCE@SOIC8 [CX1030]  
MC9S08SH4VSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH4VTG@TSSOP16 [CX1000]  
MC9S08SH4VTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH4VTGE@TSSOP16 [CX1000]  
MC9S08SH4VTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH4VTJ@TSSOP20 [CX1000]  
MC9S08SH4VTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH4VTJE@TSSOP20 [CX1000]

MC9S08SH4VTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH4VWJ@SOIC20 [CX1033]  
MC9S08SH4VWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH4VWJE@SOIC20 [CX1033]  
MC9S08SH4VWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH8CFK@QFN24 [CX4012]  
MC9S08SH8CFK@QFN24(auto trim) [CX4012]  
MC9S08SH8CFKE@QFN24 [CX4012]  
MC9S08SH8CFKE@QFN24(auto trim) [CX4012]  
MC9S08SH8CPJ MC9S08SH8CPJ(auto trim)  
MC9S08SH8CPJE MC9S08SH8CPJE(auto trim)  
MC9S08SH8CSC@SOIC8 [CX1030]  
MC9S08SH8CSC@SOIC8(auto trim) [CX1030]  
MC9S08SH8CSCE@SOIC8 [CX1030]  
MC9S08SH8CSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH8CTG@TSSOP16 [CX1000]  
MC9S08SH8CTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH8CTGE@TSSOP16 [CX1000]  
MC9S08SH8CTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH8CTJ@TSSOP20 [CX1000]  
MC9S08SH8CTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH8CTJE@TSSOP20 [CX1000]  
MC9S08SH8CTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH8CWJ@SOIC20 [CX1033]  
MC9S08SH8CWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH8CWJE@SOIC20 [CX1033]  
MC9S08SH8CWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH8MFK@QFN24 [CX4012]  
MC9S08SH8MFK@QFN24(auto trim) [CX4012]  
MC9S08SH8MFKE@QFN24 [CX4012]  
MC9S08SH8MFKE@QFN24(auto trim) [CX4012]  
MC9S08SH8MPJ MC9S08SH8MPJ(auto trim)  
MC9S08SH8MPJE MC9S08SH8MPJE(auto trim)  
MC9S08SH8MSC@SOIC8 [CX1030]  
MC9S08SH8MSC@SOIC8(auto trim) [CX1030]  
MC9S08SH8MSCE@SOIC8 [CX1030]  
MC9S08SH8MSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH8MTG@TSSOP16 [CX1000]  
MC9S08SH8MTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH8MTGE@TSSOP16 [CX1000]  
MC9S08SH8MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH8MTJ@TSSOP20 [CX1000]  
MC9S08SH8MTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH8MTJE@TSSOP20 [CX1000]  
MC9S08SH8MTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH8MWJ@SOIC20 [CX1033] MC9S08SH8MWJE@SOIC20 [CX1033]  
MC9S08SH8MWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH8VFK@QFN24 [CX4012]  
MC9S08SH8VFK@QFN24(auto trim) [CX4012]  
MC9S08SH8VFKE@QFN24 [CX4012]  
MC9S08SH8VFKE@QFN24(auto trim) [CX4012]  
MC9S08SH8VPJ MC9S08SH8VPJ(auto trim)  
MC9S08SH8VPJE MC9S08SH8VPJE(auto trim)  
MC9S08SH8VSC@SOIC8 [CX1030]  
MC9S08SH8VSC@SOIC8(auto trim) [CX1030]  
MC9S08SH8VSCE@SOIC8 [CX1030]  
MC9S08SH8VSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH8VTG@TSSOP16 [CX1000]  
MC9S08SH8VTG@TSSOP16(auto trim) [CX1000]

MC9S08SH8VTGE@TSSOP16 [CX1000]  
MC9S08SH8VTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH8VTJ@TSSOP20 [CX1000]  
MC9S08SH8VTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH8VTJE@TSSOP20 [CX1000]  
MC9S08SH8VTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH8VWJ@SOIC20 [CX1033]  
MC9S08SH8VWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH8VWJE@SOIC20 [CX1033]  
MC9S08SH8VWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH9MWJ@SOIC20(auto trim) [CX1033]  
MC9S08SL16CTJ@TSSOP20 [CX1000]            MC9S08SL16CTJE@TSSOP20 [CX1000]  
MC9S08SL16CTL@TSSOP28 [CX1001]            MC9S08SL16CTLE@TSSOP28 [CX1001]  
MC9S08SL16MTJ@TSSOP20 [CX1000]            MC9S08SL16MTJE@TSSOP20 [CX1000]  
MC9S08SL16MTL@TSSOP28 [CX1001]            MC9S08SL16MTLE@TSSOP28 [CX1001]  
MC9S08SL16VTJ@TSSOP20 [CX1000]            MC9S08SL16VTJE@TSSOP20 [CX1000]  
MC9S08SL16VTL@TSSOP28 [CX1001]            MC9S08SL16VTLE@TSSOP28 [CX1001]  
MC9S08SL8CTJ@TSSOP20 [CX1000]            MC9S08SL8CTJE@TSSOP20 [CX1000]  
MC9S08SL8CTL@TSSOP28 [CX1001]            MC9S08SL8CTLE@TSSOP28 [CX1001]  
MC9S08SL8MTJ@TSSOP20 [CX1000]            MC9S08SL8MTJE@TSSOP20 [CX1000]  
MC9S08SL8MTL@TSSOP28 [CX1001]            MC9S08SL8MTLE@TSSOP28 [CX1001]  
MC9S08SL8VTJ@TSSOP20 [CX1000]            MC9S08SL8VTJE@TSSOP20 [CX1000]  
MC9S08SL8VTL@TSSOP28 [CX1001]            MC9S08SL8VTLE@TSSOP28 [CX1001]  
MC9S08SV16CBM@SDIP32 [CX0032]            MC9S08SV16CLC@LQFP32 [CX3001]  
MC9S08SV16MBM@SDIP32 [CX0032]            MC9S08SV16MLC@LQFP32 [CX3001]  
MC9S08SV16VBM@SDIP32 [CX0032]            MC9S08SV16VLC@LQFP32 [CX3001]  
MC9S08SV8CBM@SDIP32 [CX0032]            MC9S08SV8CLC@LQFP32 [CX3001]  
MC9S08SV8MBM@SDIP32 [CX0032]            MC9S08SV8MLC@LQFP32 [CX3001]  
MC9S08SV8VBM@SDIP32 [CX0032]            MC9S08SV8VLC@LQFP32 [CX3001]  
MC9S12A128BCFU@TQFP80 [CX3018]            MC9S12A128BMFU@TQFP80 [CX3018]  
MC9S12A128BVFU@TQFP80 [CX3018]            MC9S12A128CFU@TQFP80 [CX3018]  
MC9S12A128MFU@TQFP80 [CX3018]            MC9S12A128VFU@TQFP80 [CX3018]  
MC9S12A256BCFU@TQFP80 [CX3018]            MC9S12A256BMFU@TQFP80 [CX3018]  
MC9S12A256BVFU@TQFP80 [CX3018]            MC9S12A256CFU@TQFP80 [CX3018]  
MC9S12A256MFU@TQFP80 [CX3018]            MC9S12A256VFU@TQFP80 [CX3018]  
MC9S12A64CFU@TQFP80 [CX3018]            MC9S12A64MFU@TQFP80 [CX3018]  
MC9S12A64VFU@TQFP80 [CX3018]            MC9S12B128CFU@TQFP80 [CX3018]  
MC9S12B128MFU@TQFP80 [CX3018]            MC9S12B128VFU@TQFP80 [CX3018]  
MC9S12B256CFU@TQFP80 [CX3018]            MC9S12B256MFU@TQFP80 [CX3018]  
MC9S12B256VFU@TQFP80 [CX3018]            MC9S12B64CFU@TQFP80 [CX3018]  
MC9S12B64MFU@TQFP80 [CX3018]            MC9S12B64VFU@TQFP80 [CX3018]  
MC9S12C128CFA@TQFP48 [CX3007]            MC9S12C128CFU@TQFP80 [CX3018]  
MC9S12C128CPB@TQFP52 [CX3010]            MC9S12C128MFA@TQFP48 [CX3007]  
MC9S12C128MFU@TQFP80 [CX3018]            MC9S12C128MPB@TQFP52 [CX3010]  
MC9S12C128VFA@TQFP48 [CX3007]            MC9S12C128VFU@TQFP80 [CX3018]  
MC9S12C128VPB@TQFP52 [CX3010]            MC9S12C32CFA16@TQFP48 [CX3007]  
MC9S12C32CFA25@TQFP48 [CX3007]            MC9S12C32CFU16@TQFP80 [CX3018]  
MC9S12C32CFU25@TQFP80 [CX3018]            MC9S12C32CPB16@TQFP52 [CX3010]  
MC9S12C32CPB25@TQFP52 [CX3010]            MC9S12C32MFA16@TQFP48 [CX3007]  
MC9S12C32MFA25@TQFP48 [CX3007]            MC9S12C32MFU16@TQFP80 [CX3018]  
MC9S12C32MFU25@TQFP80 [CX3018]            MC9S12C32MPB16@TQFP52 [CX3010]  
MC9S12C32MPB25@TQFP52 [CX3010]            MC9S12C32VFA16@TQFP48 [CX3007]  
MC9S12C32VFA25@TQFP48 [CX3007]            MC9S12C32VFU16@TQFP80 [CX3018]  
MC9S12C32VFU25@TQFP80 [CX3018]            MC9S12C32VPB16@TQFP52 [CX3010]  
MC9S12C32VPB25@TQFP52 [CX3010]            MC9S12C64CFA@TQFP48 [CX3007]  
MC9S12C64CFU@TQFP80 [CX3018]            MC9S12C64CPB@TQFP52 [CX3010]  
MC9S12C64MFA@TQFP48 [CX3007]            MC9S12C64MFU@TQFP80 [CX3018]  
MC9S12C64MPB@TQFP52 [CX3010]            MC9S12C64VFA@TQFP48 [CX3007]  
MC9S12C64VFU@TQFP80 [CX3018]            MC9S12C64VPB@TQFP52 [CX3010]

MC9S12C96CFA@TQFP48 [CX3007]  
MC9S12C96CPB@TQFP52 [CX3010]  
MC9S12C96MFU@TQFP80 [CX3018]  
MC9S12C96VFA@TQFP48 [CX3007]  
MC9S12C96VPB@TQFP52 [CX3010]  
MC9S12D32MFU@TQFP80 [CX3018]  
MC9S12D64CFU@TQFP80 [CX3018]  
MC9S12D64VFU@TQFP80 [CX3018]  
MC9S12DB128BMFU@TQFP80 [CX3018]  
MC9S12DB128CFU@TQFP80 [CX3018]  
MC9S12DB128VFU@TQFP80 [CX3018]  
MC9S12DG128BMFU@TQFP80 [CX3018]  
MC9S12DG128CFU@TQFP80 [CX3018]  
MC9S12DG128EMFU@TQFP80 [CX3018]  
MC9S12DG128MFU@TQFP80 [CX3018]  
MC9S12DG256BCFU@TQFP80 [CX3018]  
MC9S12DG256BVFU@TQFP80 [CX3018]  
MC9S12DG256CFU@TQFP80 [CX3018]  
MC9S12DG256CVFU@TQFP80 [CX3018]  
MC9S12DG256VFU@TQFP80 [CX3018]  
MC9S12DJ128BMFU@TQFP80 [CX3018]  
MC9S12DJ128CFU@TQFP80 [CX3018]  
MC9S12DJ128EMFU@TQFP80 [CX3018]  
MC9S12DJ128MFU@TQFP80 [CX3018]  
MC9S12DJ256BCFU@TQFP80 [CX3018]  
MC9S12DJ256BVFU@TQFP80 [CX3018]  
MC9S12DJ256CFU@TQFP80 [CX3018]  
MC9S12DJ256CVFU@TQFP80 [CX3018]  
MC9S12DJ256VFU@TQFP80 [CX3018]  
MC9S12DJ64MFU@TQFP80 [CX3018]  
MC9S12DP256BCFU@TQFP80 [CX3018]  
MC9S12DP256BVFU@TQFP80 [CX3018]  
MC9S12DP256CMFU@TQFP80 [CX3018]  
MC9S12DT128BCFU@TQFP80 [CX3018]  
MC9S12DT128BVFU@TQFP80 [CX3018]  
MC9S12DT128ECFU@TQFP80 [CX3018]  
MC9S12DT128EVFU@TQFP80 [CX3018]  
MC9S12DT128VFU@TQFP80 [CX3018]  
MC9S12DT256BMFU@TQFP80 [CX3018]  
MC9S12DT256CCFU@TQFP80 [CX3018]  
MC9S12DT256CMFU@TQFP80 [CX3018]  
MC9S12DT256MFU@TQFP80 [CX3018]  
MC9S12E128CFU@TQFP80 [CX3018]  
MC9S12E128MFU@TQFP80 [CX3018]  
MC9S12E128VFU@TQFP80 [CX3018]  
MC9S12E256CFU@TQFP80 [CX3018]  
MC9S12E256MFU@TQFP80 [CX3018]  
MC9S12E256VFU@TQFP80 [CX3018]  
MC9S12E32CFC@TQFP64 [CX4023]  
MC9S12E32CFU@TQFP80 [CX3018]  
MC9S12E32MFC@TQFP64 [CX4023]  
MC9S12E32MFU@TQFP80 [CX3018]  
MC9S12E32VFC@TQFP64 [CX4023]  
MC9S12E32VFU@TQFP80 [CX3018]  
MC9S12E64CFU@TQFP80 [CX3018]  
MC9S12E64MFU@TQFP80 [CX3018]  
MC9S12E64VFU@TQFP80 [CX3018]  
MC9S12GC128CFA@TQFP48 [CX3007]  
MC9S12GC128CPB@TQFP52 [CX3010]

MC9S12C96CFU@TQFP80 [CX3018]  
MC9S12C96MFA@TQFP48 [CX3007]  
MC9S12C96MPB@TQFP52 [CX3010]  
MC9S12C96VFU@TQFP80 [CX3018]  
MC9S12D32CFU@TQFP80 [CX3018]  
MC9S12D32VFU@TQFP80 [CX3018]  
MC9S12D64MFU@TQFP80 [CX3018]  
MC9S12DB128BCFU@TQFP80 [CX3018]  
MC9S12DB128BVFU@TQFP80 [CX3018]  
MC9S12DB128MFU@TQFP80 [CX3018]  
MC9S12DG128BCFU@TQFP80 [CX3018]  
MC9S12DG128BVFU@TQFP80 [CX3018]  
MC9S12DG128ECFU@TQFP80 [CX3018]  
MC9S12DG128EVFU@TQFP80 [CX3018]  
MC9S12DG128VFU@TQFP80 [CX3018]  
MC9S12DG256BMFU@TQFP80 [CX3018]  
MC9S12DG256CCFU@TQFP80 [CX3018]  
MC9S12DG256CMFU@TQFP80 [CX3018]  
MC9S12DG256MFU@TQFP80 [CX3018]  
MC9S12DJ128BCFU@TQFP80 [CX3018]  
MC9S12DJ128BVFU@TQFP80 [CX3018]  
MC9S12DJ128ECFU@TQFP80 [CX3018]  
MC9S12DJ128EVFU@TQFP80 [CX3018]  
MC9S12DJ128VFU@TQFP80 [CX3018]  
MC9S12DJ256BMFU@TQFP80 [CX3018]  
MC9S12DJ256CCFU@TQFP80 [CX3018]  
MC9S12DJ256CMFU@TQFP80 [CX3018]  
MC9S12DJ256MFU@TQFP80 [CX3018]  
MC9S12DJ64CFU@TQFP80 [CX3018]  
MC9S12DJ64VFU@TQFP80 [CX3018]  
MC9S12DP256BMFU@TQFP80 [CX3018]  
MC9S12DP256CCFU@TQFP80 [CX3018]  
MC9S12DP256CVFU@TQFP80 [CX3018]  
MC9S12DT128BMFU@TQFP80 [CX3018]  
MC9S12DT128CFU@TQFP80 [CX3018]  
MC9S12DT128EMFU@TQFP80 [CX3018]  
MC9S12DT128MFU@TQFP80 [CX3018]  
MC9S12DT256BCFU@TQFP80 [CX3018]  
MC9S12DT256BVFU@TQFP80 [CX3018]  
MC9S12DT256CFU@TQFP80 [CX3018]  
MC9S12DT256CVFU@TQFP80 [CX3018]  
MC9S12DT256VFU@TQFP80 [CX3018]  
MC9S12E128CFUE@TQFP80 [CX3018]  
MC9S12E128MFUE@TQFP80 [CX3018]  
MC9S12E128VFUE@TQFP80 [CX3018]  
MC9S12E256CFUE@TQFP80 [CX3018]  
MC9S12E256MFUE@TQFP80 [CX3018]  
MC9S12E256VFUE@TQFP80 [CX3018]  
MC9S12E32CFCE@TQFP64 [CX4023]  
MC9S12E32CFUE@TQFP80 [CX3018]  
MC9S12E32MFCE@TQFP64 [CX4023]  
MC9S12E32MFUE@TQFP80 [CX3018]  
MC9S12E32VFCE@TQFP64 [CX4023]  
MC9S12E32VFUE@TQFP80 [CX3018]  
MC9S12E64CFUE@TQFP80 [CX3018]  
MC9S12E64MFUE@TQFP80 [CX3018]  
MC9S12E64VFUE@TQFP80 [CX3018]  
MC9S12GC128CFU@TQFP80 [CX3018]  
MC9S12GC128MFA@TQFP48 [CX3007]

MC9S12GC128MFU@TQFP80 [CX3018]      MC9S12GC128MPB@TQFP52 [CX3010]  
MC9S12GC128VFA@TQFP48 [CX3007]      MC9S12GC128VFU@TQFP80 [CX3018]  
MC9S12GC128VPB@TQFP52 [CX3010]      MC9S12GC16CFA@TQFP48 [CX3007]  
MC9S12GC16CFU@TQFP80 [CX3018]      MC9S12GC16CPB@TQFP52 [CX3010]  
MC9S12GC16MFA@TQFP48 [CX3007]      MC9S12GC16MFU@TQFP80 [CX3018]  
MC9S12GC16MPB@TQFP52 [CX3010]      MC9S12GC16VFA@TQFP48 [CX3007]  
MC9S12GC16VFU@TQFP80 [CX3018]      MC9S12GC16VPB@TQFP52 [CX3010]  
MC9S12GC32CFA@TQFP48 [CX3007]      MC9S12GC32CFU@TQFP80 [CX3018]  
MC9S12GC32CPB@TQFP52 [CX3010]      MC9S12GC32MFA@TQFP48 [CX3007]  
MC9S12GC32MFU@TQFP80 [CX3018]      MC9S12GC32MPB@TQFP52 [CX3010]  
MC9S12GC32VFA@TQFP48 [CX3007]      MC9S12GC32VFU@TQFP80 [CX3018]  
MC9S12GC32VPB@TQFP52 [CX3010]      MC9S12GC64CFA@TQFP48 [CX3007]  
MC9S12GC64CFU@TQFP80 [CX3018]      MC9S12GC64CPB@TQFP52 [CX3010]  
MC9S12GC64MFA@TQFP48 [CX3007]      MC9S12GC64MFU@TQFP80 [CX3018]  
MC9S12GC64MPB@TQFP52 [CX3010]      MC9S12GC64VFA@TQFP48 [CX3007]  
MC9S12GC64VFU@TQFP80 [CX3018]      MC9S12GC64VPB@TQFP52 [CX3010]  
MC9S12GC96CFA@TQFP48 [CX3007]      MC9S12GC96CFU@TQFP80 [CX3018]  
MC9S12GC96CPB@TQFP52 [CX3010]      MC9S12GC96MFA@TQFP48 [CX3007]  
MC9S12GC96MFU@TQFP80 [CX3018]      MC9S12GC96MPB@TQFP52 [CX3010]  
MC9S12GC96VFA@TQFP48 [CX3007]      MC9S12GC96VFU@TQFP80 [CX3018]  
MC9S12GC96VPB@TQFP52 [CX3010]      MC9S12Q128CFA@TQFP48 [CX3007]  
MC9S12Q128CFAE@TQFP48 [CX3007]      MC9S12Q128CFU@TQFP80 [CX3018]  
MC9S12Q128CFUE@TQFP80 [CX3018]      MC9S12Q128CPB@TQFP52 [CX3010]  
MC9S12Q128CPBE@TQFP52 [CX3010]      MC9S12Q128MFA@TQFP48 [CX3007]  
MC9S12Q128MFAE@TQFP48 [CX3007]      MC9S12Q128MFU@TQFP80 [CX3018]  
MC9S12Q128MFUE@TQFP80 [CX3018]      MC9S12Q128MPB@TQFP52 [CX3010]  
MC9S12Q128MPBE@TQFP52 [CX3010]      MC9S12Q128VFA@TQFP48 [CX3007]  
MC9S12Q128VFAB@TQFP48 [CX3007]      MC9S12Q128VFU@TQFP80 [CX3018]  
MC9S12Q128VFUE@TQFP80 [CX3018]      MC9S12Q128VPB@TQFP52 [CX3010]  
MC9S12Q128VPBE@TQFP52 [CX3010]      MC9S12Q32CFA@TQFP48 [CX3007]  
MC9S12Q32CFAE@TQFP48 [CX3007]      MC9S12Q32CFU@TQFP80 [CX3018]  
MC9S12Q32CFUE@TQFP80 [CX3018]      MC9S12Q32CPB@TQFP52 [CX3010]  
MC9S12Q32CPBE@TQFP52 [CX3010]      MC9S12Q32MFA@TQFP48 [CX3007]  
MC9S12Q32MFAE@TQFP48 [CX3007]      MC9S12Q32MFU@TQFP80 [CX3018]  
MC9S12Q32MFUE@TQFP80 [CX3018]      MC9S12Q32MPB@TQFP52 [CX3010]  
MC9S12Q32MPBE@TQFP52 [CX3010]      MC9S12Q32VFA@TQFP48 [CX3007]  
MC9S12Q32VFAE@TQFP48 [CX3007]      MC9S12Q32VFU@TQFP80 [CX3018]  
MC9S12Q32VFUE@TQFP80 [CX3018]      MC9S12Q32VPB@TQFP52 [CX3010]  
MC9S12Q32VPBE@TQFP52 [CX3010]      MC9S12Q64CFA@TQFP48 [CX3007]  
MC9S12Q64CFAE@TQFP48 [CX3007]      MC9S12Q64CFU@TQFP80 [CX3018]  
MC9S12Q64CFUE@TQFP80 [CX3018]      MC9S12Q64CPB@TQFP52 [CX3010]  
MC9S12Q64CPBE@TQFP52 [CX3010]      MC9S12Q64MFA@TQFP48 [CX3007]  
MC9S12Q64MFAE@TQFP48 [CX3007]      MC9S12Q64MFU@TQFP80 [CX3018]  
MC9S12Q64MFUE@TQFP80 [CX3018]      MC9S12Q64MPB@TQFP52 [CX3010]  
MC9S12Q64MPBE@TQFP52 [CX3010]      MC9S12Q64VFA@TQFP48 [CX3007]  
MC9S12Q64VFAB@TQFP48 [CX3007]      MC9S12Q64VFU@TQFP80 [CX3018]  
MC9S12Q64VFUE@TQFP80 [CX3018]      MC9S12Q64VPB@TQFP52 [CX3010]  
MC9S12Q64VPBE@TQFP52 [CX3010]      MC9S12Q96CFA@TQFP48 [CX3007]  
MC9S12Q96CFAE@TQFP48 [CX3007]      MC9S12Q96CFU@TQFP80 [CX3018]  
MC9S12Q96CFUE@TQFP80 [CX3018]      MC9S12Q96CPB@TQFP52 [CX3010]  
MC9S12Q96CPBE@TQFP52 [CX3010]      MC9S12Q96MFA@TQFP48 [CX3007]  
MC9S12Q96MFAE@TQFP48 [CX3007]      MC9S12Q96MFU@TQFP80 [CX3018]  
MC9S12Q96MFUE@TQFP80 [CX3018]      MC9S12Q96MPB@TQFP52 [CX3010]  
MC9S12Q96MPBE@TQFP52 [CX3010]      MC9S12Q96VFA@TQFP48 [CX3007]  
MC9S12Q96VFAB@TQFP48 [CX3007]      MC9S12Q96VFU@TQFP80 [CX3018]  
MC9S12Q96VFUE@TQFP80 [CX3018]      MC9S12Q96VPB@TQFP52 [CX3010]  
MC9S12Q96VPBE@TQFP52 [CX3010]      MC9S12XS128CAA@QFP80 [CX3018]  
MC9S12XS128CAE@QFP64 [CX3011]      MC9S12XS128MAA@QFP80 [CX3018]  
MC9S12XS128MAE@QFP64 [CX3011]      MC9S12XS128VAA@QFP80 [CX3018]



MC9S12XS128VAE@QFP64 [CX3011]      MC9S12XS256CAA@QFP80 [CX3018]  
MC9S12XS256CAE@QFP64 [CX3011]      MC9S12XS256MAA@QFP80 [CX3018]  
MC9S12XS256MAE@QFP64 [CX3011]      MC9S12XS256VAA@QFP80 [CX3018]  
MC9S12XS256VAE@QFP64 [CX3011]      MC9S12XS64CAA@QFP80 [CX3018]  
MC9S12XS64CAE@QFP64 [CX3011]      MC9S12XS64MAA@QFP80 [CX3018]  
MC9S12XS64MAE@QFP64 [CX3011]      MC9S12XS64VAA@QFP80 [CX3018]  
MC9S12XS64VAE@QFP64 [CX3011]      MCF51AC128ACFUE@QFP64 [CX3014]  
MCF51AC128ACLKE@LQFP80 [CX3017]      MCF51AC128ACPUE@LQFP64 [CX3011]  
MCF51AC128AMFUE@QFP64 [CX3014]      MCF51AC128AMLKE@LQFP80 [CX3017]  
MCF51AC128AMPUE@LQFP64 [CX3011]      MCF51AC128AVFUE@QFP64 [CX3014]  
MCF51AC128AVLKE@LQFP80 [CX3017]      MCF51AC128AVPUE@LQFP64 [CX3011]  
MCF51AC128BCFUE@QFP64 [CX3014]      MCF51AC128BCLKE@LQFP80 [CX3017]  
MCF51AC128BCPUE@LQFP64 [CX3011]      MCF51AC128BMFUE@QFP64 [CX3014]  
MCF51AC128BMLKE@LQFP80 [CX3017]      MCF51AC128BMPUE@LQFP64 [CX3011]  
MCF51AC128BVFUE@QFP64 [CX3014]      MCF51AC128BVLKE@LQFP80 [CX3017]  
MCF51AC128BVPUE@LQFP64 [CX3011]      MCF51AC128CCFUE@QFP64 [CX3014]  
MCF51AC128CCLKE@LQFP80 [CX3017]      MCF51AC128CCPUE@LQFP64 [CX3011]  
MCF51AC128CMFUE@QFP64 [CX3014]      MCF51AC128CMLKE@LQFP80 [CX3017]  
MCF51AC128CMPUE@LQFP64 [CX3011]      MCF51AC128CVFUE@QFP64 [CX3014]  
MCF51AC128CVLKE@LQFP80 [CX3017]      MCF51AC128CVPUE@LQFP64 [CX3011]  
MCF51AC256ACFUE@QFP64 [CX3014]      MCF51AC256ACLKE@LQFP80 [CX3017]  
MCF51AC256ACPUE@LQFP64 [CX3011]      MCF51AC256AMFUE@QFP64 [CX3014]  
MCF51AC256AMLKE@LQFP80 [CX3017]      MCF51AC256AMPUE@LQFP64 [CX3011]  
MCF51AC256AVFUE@QFP64 [CX3014]      MCF51AC256AVLKE@LQFP80 [CX3017]  
MCF51AC256AVPUE@LQFP64 [CX3011]      MCF51AC256BCFUE@QFP64 [CX3014]  
MCF51AC256BCLKE@LQFP80 [CX3017]      MCF51AC256BCPUE@LQFP64 [CX3011]  
MCF51AC256BMFUE@QFP64 [CX3014]      MCF51AC256BMLKE@LQFP80 [CX3017]  
MCF51AC256BMPUE@LQFP64 [CX3011]      MCF51AC256BVFUE@QFP64 [CX3014]  
MCF51AC256BVLKE@LQFP80 [CX3017]      MCF51AC256BVPUE@LQFP64 [CX3011]  
MCF51AC256CCFUE@QFP64 [CX3014]      MCF51AC256CCLKE@LQFP80 [CX3017]  
MCF51AC256CCPUE@LQFP64 [CX3011]      MCF51AC256CMFUE@QFP64 [CX3014]  
MCF51AC256CMLKE@LQFP80 [CX3017]      MCF51AC256CMPUE@LQFP64 [CX3011]  
MCF51AC256CVFUE@QFP64 [CX3014]      MCF51AC256CVLKE@LQFP80 [CX3017]  
MCF51AC256CVPUE@LQFP64 [CX3011]      MCF51CN128CGT@QFN48 [CX4021]  
MCF51CN128CLH@LQFP64 [CX3011]      MCF51CN128CLK@LQFP80 [CX3017]  
MCF51CN128MGT@QFN48 [CX4021]      MCF51CN128MLH@LQFP64 [CX3011]  
MCF51CN128MLK@LQFP80 [CX3017]      MCF51CN128VGT@QFN48 [CX4021]  
MCF51CN128VLH@LQFP64 [CX3011]      MCF51CN128VLK@LQFP80 [CX3017]  
MCF51JE128CLK@QFP80 [CX3016]      MCF51JE128CLL@QFP100 [CX3021]  
MCF51JE128MLK@QFP80 [CX3016]      MCF51JE128MLL@QFP100 [CX3021]  
MCF51JE128VLK@QFP80 [CX3016]      MCF51JE128VLL@QFP100 [CX3021]  
MCF51JE256CLK@QFP80 [CX3016]      MCF51JE256CLL@QFP100 [CX3021]  
MCF51JE256MLK@QFP80 [CX3016]      MCF51JE256MLL@QFP100 [CX3021]  
MCF51JE256VLK@QFP80 [CX3016]      MCF51JE256VLL@QFP100 [CX3021]  
MCF51JF128VLH@QFP64 [CX3011]      MCF51JM128CLD@LQFP44 [CX3005]  
MCF51JM128CLH@LQFP64 [CX3011]      MCF51JM128CLK@LQFP80 [CX3017]  
MCF51JM128CQH@QFP64 [CX3014]      MCF51JM128ECLK@LQFP80 [CX3017]  
MCF51JM128EMLK@LQFP80 [CX3017]      MCF51JM128EVLK@LQFP80 [CX3017]  
MCF51JM128MLD@LQFP44 [CX3005]      MCF51JM128MLH@LQFP64 [CX3011]  
MCF51JM128MLK@LQFP80 [CX3017]      MCF51JM128MQH@QFP64 [CX3014]  
MCF51JM128VLD@LQFP44 [CX3005]      MCF51JM128VLH@LQFP64 [CX3011]  
MCF51JM128VLK@LQFP80 [CX3017]      MCF51JM128VQH@QFP64 [CX3014]  
MCF51JM32CLD@LQFP44 [CX3005]      MCF51JM32CLH@LQFP64 [CX3011]  
MCF51JM32CLK@LQFP80 [CX3017]      MCF51JM32CQH@QFP64 [CX3014]  
MCF51JM32ECLK@LQFP80 [CX3017]      MCF51JM32EMLK@LQFP80 [CX3017]  
MCF51JM32EVLK@LQFP80 [CX3017]      MCF51JM32MLD@LQFP44 [CX3005]  
MCF51JM32MLH@LQFP64 [CX3011]      MCF51JM32MLK@LQFP80 [CX3017]  
MCF51JM32MQH@QFP64 [CX3014]      MCF51JM32VLD@LQFP44 [CX3005]  
MCF51JM32VLH@LQFP64 [CX3011]      MCF51JM32VLK@LQFP80 [CX3017]

MCF51JM32VQH@QFP64 [CX3014]  
MCF51JM64CLH@LQFP64 [CX3011]  
MCF51JM64CQH@QFP64 [CX3014]  
MCF51JM64EMLK@LQFP80 [CX3017]  
MCF51JM64MLD@LQFP44 [CX3005]  
MCF51JM64MLK@LQFP80 [CX3017]  
MCF51JM64VLD@LQFP44 [CX3005]  
MCF51JM64VLK@LQFP80 [CX3017]  
MCF51JU128VLH@QFP64 [CX3011]  
MCF51QE128CLK@QFP80 [CX3017]  
MCF51QE128LK@QFP80 [CX3017]  
MCF51QE128MLK@QFP80 [CX3017]  
MCF51QE128VLK@QFP80 [CX3017]  
MCF51QE32CLK@QFP80 [CX3017]  
MCF51QE32LK@QFP80 [CX3017]  
MCF51QE32MLK@QFP80 [CX3017]  
MCF51QE32VLK@QFP80 [CX3017]  
MCF51QE64CLK@QFP80 [CX3017]  
MCF51QE64LK@QFP80 [CX3017]  
MCF51QE64MLK@QFP80 [CX3017]  
MCF51QE64VLK@QFP80 [CX3017]  
MCF51QE96CLK@QFP80 [CX3017]  
MCF51QE96LK@QFP80 [CX3017]  
MCF51QE96MLK@QFP80 [CX3017]  
MCF51QE96VLK@QFP80 [CX3017]  
MCHC908JW32FC@TQFN48 [CX4021]  
MM908E621ACDWB@SOIC54 [CX1060]  
MM908E624ACDWB@SOIC54 [CX1060]  
MM908E624AYEW@SOIC54 [CX1060]  
MM908E625AVEK@SOIC54 [CX1060]  
MM908E626AVEK@SOIC54 [CX1060]  
MM912F634BC2AE@QFP48 [CX3007-2]  
MM912F634BV1AE@QFP48 [CX3007-2]  
MM912F634BV3AE@QFP48 [CX3007-2]  
MM912F634CV2AE@QFP48 [CX3007-2]  
PC56F8011VFAE@QFP32 [CX3001]  
PC56F8014VFAE@QFP32 [CX3001]  
PC9S08SG4CSCE@SOIC8 [CX1030]  
PC9S08SG4CTGE@TSSOP16 [CX1000]  
PC9S08SG4CTJE@TSSOP20 [CX1000]  
PC9S08SG4MSCE@SOIC8 [CX1030]  
PC9S08SG4MTGE@TSSOP16 [CX1000]  
PC9S08SG4MTJE@TSSOP20 [CX1000]  
PC9S08SG4VSCE@SOIC8 [CX1030]  
PC9S08SG4VTGE@TSSOP16 [CX1000]  
PC9S08SG4VTJE@TSSOP20 [CX1000]  
PC9S08SG8CSCE@SOIC8 [CX1030]  
PC9S08SG8CTGE@TSSOP16 [CX1000]  
PC9S08SG8CTJE@TSSOP20 [CX1000]  
PC9S08SG8MSCE@SOIC8 [CX1030]  
PC9S08SG8MTGE@TSSOP16 [CX1000]  
PC9S08SG8MTJE@TSSOP20 [CX1000]  
PC9S08SG8VSCE@SOIC8 [CX1030]  
PC9S08SG8VTGE@TSSOP16 [CX1000]  
PC9S08SG8VTJE@TSSOP20 [CX1000]  
PC9S08SH4CFK@QFN24(auto trim) [CX4012]  
PC9S08SH4CFKE@QFN24 [CX4012]  
PC9S08SH4CFKE@QFN24(auto trim) [CX4012]  
PC9S08SH4CPJ  
MCF51JM64CLD@LQFP44 [CX3005]  
MCF51JM64CLK@LQFP80 [CX3017]  
MCF51JM64ECLK@LQFP80 [CX3017]  
MCF51JM64EVLK@LQFP80 [CX3017]  
MCF51JM64MLH@LQFP64 [CX3011]  
MCF51JM64MQH@QFP64 [CX3014]  
MCF51JM64VLH@LQFP64 [CX3011]  
MCF51JM64VQH@QFP64 [CX3014]  
MCF51QE128CLH@QFP64 [CX3011]  
MCF51QE128LH@QFP64 [CX3011]  
MCF51QE128MLH@QFP64 [CX3011]  
MCF51QE128VLH@QFP64 [CX3011]  
MCF51QE32CLH@QFP64 [CX3011]  
MCF51QE32LH@QFP64 [CX3011]  
MCF51QE32MLH@QFP64 [CX3011]  
MCF51QE32VLH@QFP64 [CX3011]  
MCF51QE64CLH@QFP64 [CX3011]  
MCF51QE64LH@QFP64 [CX3011]  
MCF51QE64MLH@QFP64 [CX3011]  
MCF51QE64VLH@QFP64 [CX3011]  
MCF51QE96CLH@QFP64 [CX3011]  
MCF51QE96LH@QFP64 [CX3011]  
MCF51QE96MLH@QFP64 [CX3011]  
MCF51QE96VLH@QFP64 [CX3011]  
MCF51QM128VLH@QFP64 [CX3011]  
MCHC908JW32FCE@TQFN48 [CX4021]  
MM908E622ACDWB@SOIC54 [CX1060]  
MM908E624ACEW@SOIC54 [CX1060]  
MM908E625AVDWB@SOIC54 [CX1060]  
MM908E626AVDWB@SOIC54 [CX1060]  
MM912F634BC1AE@QFP48 [CX3007-2]  
MM912F634BC3AE@QFP48 [CX3007-2]  
MM912F634BV2AE@QFP48 [CX3007-2]  
MM912F634CV1AE@QFP48 [CX3007-2]  
MM912F634CV2AP@QFP48 [CX3007-2]  
PC56F8013VFAE@QFP32 [CX3001]  
PC9S08SG4CSC@SOIC8 [CX1030]  
PC9S08SG4CTG@TSSOP16 [CX1000]  
PC9S08SG4CTJ@TSSOP20 [CX1000]  
PC9S08SG4MSC@SOIC8 [CX1030]  
PC9S08SG4MTG@TSSOP16 [CX1000]  
PC9S08SG4MTJ@TSSOP20 [CX1000]  
PC9S08SG4VSC@SOIC8 [CX1030]  
PC9S08SG4VTG@TSSOP16 [CX1000]  
PC9S08SG4VTJ@TSSOP20 [CX1000]  
PC9S08SG8CSC@SOIC8 [CX1030]  
PC9S08SG8CTG@TSSOP16 [CX1000]  
PC9S08SG8CTJ@TSSOP20 [CX1000]  
PC9S08SG8MSC@SOIC8 [CX1030]  
PC9S08SG8MTG@TSSOP16 [CX1000]  
PC9S08SG8MTJ@TSSOP20 [CX1000]  
PC9S08SG8VSC@SOIC8 [CX1030]  
PC9S08SG8VTG@TSSOP16 [CX1000]  
PC9S08SG8VTJ@TSSOP20 [CX1000]  
PC9S08SH4CFK@QFN24 [CX4012]

PC9S08SH4CPJE PC9S08SH4CPJE(auto trim)  
PC9S08SH4CSC@SOIC8 [CX1030]  
PC9S08SH4CSC@SOIC8(auto trim) [CX1030]  
PC9S08SH4CSCE@SOIC8 [CX1030]  
PC9S08SH4CSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH4CTG@TSSOP16 [CX1000]  
PC9S08SH4CTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH4CTGE@TSSOP16 [CX1000]  
PC9S08SH4CTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH4CTJ@TSSOP20 [CX1000]  
PC9S08SH4CTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH4CTJE@TSSOP20 [CX1000]  
PC9S08SH4CTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH4CWJ@SOIC20 [CX1033]  
PC9S08SH4CWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH4CWJE@SOIC20 [CX1033]  
PC9S08SH4CWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH4MFK@QFN24 [CX4012]  
PC9S08SH4MFK@QFN24(auto trim) [CX4012]  
PC9S08SH4MFKE@QFN24 [CX4012]  
PC9S08SH4MFKE@QFN24(auto trim) [CX4012]  
PC9S08SH4MPJ PC9S08SH4MPJ(auto trim)  
PC9S08SH4MPJE PC9S08SH4MPJE(auto trim)  
PC9S08SH4MSC@SOIC8 [CX1030]  
PC9S08SH4MSC@SOIC8(auto trim) [CX1030]  
PC9S08SH4MSCE@SOIC8 [CX1030]  
PC9S08SH4MSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH4MTG@TSSOP16 [CX1000]  
PC9S08SH4MTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH4MTGE@TSSOP16 [CX1000]  
PC9S08SH4MTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH4MTJ@TSSOP20 [CX1000]  
PC9S08SH4MTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH4MTJE@TSSOP20 [CX1000]  
PC9S08SH4MTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH4MWJ@SOIC20 [CX1033]  
PC9S08SH4MWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH4MWJE@SOIC20 [CX1033]  
PC9S08SH4MWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH4VFK@QFN24 [CX4012]  
PC9S08SH4VFK@QFN24(auto trim) [CX4012]  
PC9S08SH4VFKE@QFN24 [CX4012]  
PC9S08SH4VFKE@QFN24(auto trim) [CX4012]  
PC9S08SH4VPJ PC9S08SH4VPJ(auto trim)  
PC9S08SH4VPJE PC9S08SH4VPJE(auto trim)  
PC9S08SH4VSC@SOIC8 [CX1030]  
PC9S08SH4VSC@SOIC8(auto trim) [CX1030]  
PC9S08SH4VSCE@SOIC8 [CX1030]  
PC9S08SH4VSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH4VTG@TSSOP16 [CX1000]  
PC9S08SH4VTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH4VTGE@TSSOP16 [CX1000]  
PC9S08SH4VTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH4VTJ@TSSOP20 [CX1000]  
PC9S08SH4VTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH4VTJE@TSSOP20 [CX1000]  
PC9S08SH4VTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH4VWJ@SOIC20 [CX1033]  
PC9S08SH4VWJ@SOIC20(auto trim) [CX1033]

PC9S08SH4VWJE@SOIC20 [CX1033]  
PC9S08SH4VWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH8CFK@QFN24 [CX4012]  
PC9S08SH8CFK@QFN24(auto trim) [CX4012]  
PC9S08SH8CFKE@QFN24 [CX4012]  
PC9S08SH8CFKE@QFN24(auto trim) [CX4012]  
PC9S08SH8CPJ PC9S08SH8CPJ(auto trim)  
PC9S08SH8CPJE PC9S08SH8CPJE(auto trim)  
PC9S08SH8CSC@SOIC8 [CX1030]  
PC9S08SH8CSC@SOIC8(auto trim) [CX1030]  
PC9S08SH8CSCE@SOIC8 [CX1030]  
PC9S08SH8CSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH8CTG@TSSOP16 [CX1000]  
PC9S08SH8CTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH8CTGE@TSSOP16 [CX1000]  
PC9S08SH8CTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH8CTJ@TSSOP20 [CX1000]  
PC9S08SH8CTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH8CTJE@TSSOP20 [CX1000]  
PC9S08SH8CTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH8CWJ@SOIC20 [CX1033]  
PC9S08SH8CWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH8CWJE@SOIC20 [CX1033]  
PC9S08SH8CWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH8MFK@QFN24 [CX4012]  
PC9S08SH8MFK@QFN24(auto trim) [CX4012]  
PC9S08SH8MFKE@QFN24 [CX4012]  
PC9S08SH8MFKE@QFN24(auto trim) [CX4012]  
PC9S08SH8MPJ PC9S08SH8MPJ(auto trim)  
PC9S08SH8MPJE PC9S08SH8MPJE(auto trim)  
PC9S08SH8MSC@SOIC8 [CX1030]  
PC9S08SH8MSC@SOIC8(auto trim) [CX1030]  
PC9S08SH8MSCE@SOIC8 [CX1030]  
PC9S08SH8MSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH8MTG@TSSOP16 [CX1000]  
PC9S08SH8MTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH8MTGE@TSSOP16 [CX1000]  
PC9S08SH8MTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH8MTJ@TSSOP20 [CX1000]  
PC9S08SH8MTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH8MTJE@TSSOP20 [CX1000]  
PC9S08SH8MTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH8MWJ@SOIC20 [CX1033] PC9S08SH8MWJE@SOIC20 [CX1033]  
PC9S08SH8MWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH8VFK@QFN24 [CX4012]  
PC9S08SH8VFK@QFN24(auto trim) [CX4012]  
PC9S08SH8VFKE@QFN24 [CX4012]  
PC9S08SH8VFKE@QFN24(auto trim) [CX4012]  
PC9S08SH8VPJ PC9S08SH8VPJ(auto trim)  
PC9S08SH8VPJE PC9S08SH8VPJE(auto trim)  
PC9S08SH8VSC@SOIC8 [CX1030]  
PC9S08SH8VSC@SOIC8(auto trim) [CX1030]  
PC9S08SH8VSCE@SOIC8 [CX1030]  
PC9S08SH8VSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH8VTG@TSSOP16 [CX1000]  
PC9S08SH8VTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH8VTGE@TSSOP16 [CX1000]  
PC9S08SH8VTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH8VTJ@TSSOP20 [CX1000]

PC9S08SH8VTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH8VTJE@TSSOP20 [CX1000]  
PC9S08SH8VTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH8VWJ@SOIC20 [CX1033]  
PC9S08SH8VWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH8VWJE@SOIC20 [CX1033]  
PC9S08SH8VWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH9MWJ@SOIC20(auto trim) [CX1033]  
S908QY2ACDT@TSSOP16 [CX1001]  
S908QY2ACDT@TSSOP16(a trim) [CX1001]  
S908QY2ACDTE@TSSOP16 [CX1001]  
S908QY2ACDTE@TSSOP16(a trim) [CX1001]  
S908QY2ACDW@SOIC16 [CX1033]  
S908QY2ACDW@SOIC16(a trim) [CX1033]  
S908QY2ACDWE@SOIC16 [CX1033]  
S908QY2ACDWE@SOIC16(a trim) [CX1033]  
S908QY2AMDT@TSSOP16 [CX1001]  
S908QY2AMDT@TSSOP16(a trim) [CX1001]  
S908QY2AMDTE@TSSOP16 [CX1001]  
S908QY2AMDTE@TSSOP16(a trim) [CX1001]  
S908QY2AMDW@SOIC16 [CX1033]  
S908QY2AMDW@SOIC16(a trim) [CX1033]  
S908QY2AMDWE@SOIC16 [CX1033]  
S908QY2AMDWE@SOIC16(a trim) [CX1033]  
S908QY2AVDT@TSSOP16 [CX1001]  
S908QY2AVDT@TSSOP16(a trim) [CX1001]  
S908QY2AVDTE@TSSOP16 [CX1001]  
S908QY2AVDTE@TSSOP16(a trim) [CX1001]  
S908QY2AVDW@SOIC16 [CX1033]  
S908QY2AVDW@SOIC16(a trim) [CX1033]  
S908QY2AVDWE@SOIC16 [CX1033]  
S908QY2AVDWE@SOIC16(a trim) [CX1033]  
S908QY4ACDT@TSSOP16 [CX1001]  
S908QY4ACDT@TSSOP16(a trim) [CX1001]  
S908QY4ACDTE@TSSOP16 [CX1001]  
S908QY4ACDTE@TSSOP16(a trim) [CX1001]  
S908QY4ACDW@SOIC16 [CX1033]  
S908QY4ACDW@SOIC16(a trim) [CX1033]  
S908QY4ACDWE@SOIC16 [CX1033]  
S908QY4ACDWE@SOIC16(a trim) [CX1033]  
S908QY4AMDT@TSSOP16 [CX1001]  
S908QY4AMDT@TSSOP16(a trim) [CX1001]  
S908QY4AMDTE@TSSOP16 [CX1001]  
S908QY4AMDTE@TSSOP16(a trim) [CX1001]  
S908QY4AMDW@SOIC16 [CX1033]  
S908QY4AMDW@SOIC16(a trim) [CX1033]  
S908QY4AMDWE@SOIC16 [CX1033]  
S908QY4AMDWE@SOIC16(a trim) [CX1033]  
S908QY4AVDT@TSSOP16 [CX1001]  
S908QY4AVDT@TSSOP16(a trim) [CX1001]  
S908QY4AVDTE@TSSOP16 [CX1001]  
S908QY4AVDTE@TSSOP16(a trim) [CX1001]  
S908QY4AVDW@SOIC16 [CX1033]  
S908QY4AVDW@SOIC16(a trim) [CX1033]  
S908QY4AVDWE@SOIC16 [CX1033]  
S908QY4AVDWE@SOIC16(a trim) [CX1033]  
S9S08AW16ACFT [CX4021] S9S08AW16ACLM [CX3001]  
S9S08AW16ACLS [CX3003]  
S9S08AW16ACLS@QFP44(\*) [SA245A+B4404]

S9S08AW16AMFT [CX4021] S9S08AW16AMLM [CX3001]  
S9S08AW16AMLS [CX3003]  
S9S08AW16AMLS@QFP44(\*) [SA245A+B4404]  
S9S08AW16AVFT [CX4021] S9S08AW16AVLM [CX3001]  
S9S08AW16AVLS [CX3003]  
S9S08AW16AVLS@QFP44(\*) [SA245A+B4404]  
S9S08AW8ACFT [CX4021] S9S08AW8ACLM [CX3001]  
S9S08AW8ACLS [CX3003]  
S9S08AW8ACLS@QFP44(\*) [SA245A+B4404]  
S9S08AW8AMFT [CX4021] S9S08AW8AMLM [CX3001]  
S9S08AW8AMLS [CX3003]  
S9S08AW8AMLS@QFP44(\*) [SA245A+B4404]  
S9S08AW8AVFT [CX4021] S9S08AW8AVLM [CX3001]  
S9S08AW8AVLS [CX3003]  
S9S08AW8AVLS@QFP44(\*) [SA245A+B4404]  
S9S08SG4CSC@SOIC8 [CX1030] S9S08SG4CSC@SOIC8 [CX1030]  
S9S08SG4CTG@TSSOP16 [CX1000] S9S08SG4CTGE@TSSOP16 [CX1000]  
S9S08SG4CTJ@TSSOP20 [CX1000] S9S08SG4CTJE@TSSOP20 [CX1000]  
S9S08SG4MSC@SOIC8 [CX1030] S9S08SG4MSCE@SOIC8 [CX1030]  
S9S08SG4MTG@TSSOP16 [CX1000] S9S08SG4MTGE@TSSOP16 [CX1000]  
S9S08SG4MTJ@TSSOP20 [CX1000] S9S08SG4MTJE@TSSOP20 [CX1000]  
S9S08SG4VSC@SOIC8 [CX1030] S9S08SG4VSCE@SOIC8 [CX1030]  
S9S08SG4VTG@TSSOP16 [CX1000] S9S08SG4VTGE@TSSOP16 [CX1000]  
S9S08SG4VTJ@TSSOP20 [CX1000] S9S08SG4VTJE@TSSOP20 [CX1000]  
S9S08SG8CSC@SOIC8 [CX1030] S9S08SG8CSCE@SOIC8 [CX1030]  
S9S08SG8CTG@TSSOP16 [CX1000] S9S08SG8CTGE@TSSOP16 [CX1000]  
S9S08SG8CTJ@TSSOP20 [CX1000] S9S08SG8CTJE@TSSOP20 [CX1000]  
S9S08SG8MSC@SOIC8 [CX1030] S9S08SG8MSCE@SOIC8 [CX1030]  
S9S08SG8MTG@TSSOP16 [CX1000] S9S08SG8MTGE@TSSOP16 [CX1000]  
S9S08SG8MTJ@TSSOP20 [CX1000] S9S08SG8MTJE@TSSOP20 [CX1000]  
S9S08SG8VSC@SOIC8 [CX1030] S9S08SG8VSCE@SOIC8 [CX1030]  
S9S08SG8VTG@TSSOP16 [CX1000] S9S08SG8VTGE@TSSOP16 [CX1000]  
S9S08SG8VTJ@TSSOP20 [CX1000] S9S08SG8VTJE@TSSOP20 [CX1000]  
S9S08SH4CFK@QFN24 [CX4012]  
S9S08SH4CFK@QFN24(auto trim) [CX4012]  
S9S08SH4CFKE@QFN24 [CX4012]  
S9S08SH4CFKE@QFN24(auto trim) [CX4012]  
S9S08SH4CPJ S9S08SH4CPJ(auto trim)  
S9S08SH4CPJE S9S08SH4CPJE(auto trim)  
S9S08SH4CSC@SOIC8 [CX1030]  
S9S08SH4CSC@SOIC8(auto trim) [CX1030]  
S9S08SH4CSCE@SOIC8 [CX1030]  
S9S08SH4CSCE@SOIC8(auto trim) [CX1030]  
S9S08SH4CTG@TSSOP16 [CX1000]  
S9S08SH4CTG@TSSOP16(auto trim) [CX1000]  
S9S08SH4CTGE@TSSOP16 [CX1000]  
S9S08SH4CTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH4CTJ@TSSOP20 [CX1000]  
S9S08SH4CTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH4CTJE@TSSOP20 [CX1000]  
S9S08SH4CTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH4CWJ@SOIC20 [CX1033]  
S9S08SH4CWJ@SOIC20(auto trim) [CX1033]  
S9S08SH4CWJE@SOIC20 [CX1033]  
S9S08SH4CWJE@SOIC20(auto trim) [CX1033]  
S9S08SH4MFK@QFN24 [CX4012]  
S9S08SH4MFK@QFN24(auto trim) [CX4012]  
S9S08SH4MFKE@QFN24 [CX4012]  
S9S08SH4MFKE@QFN24(auto trim) [CX4012]

S9S08SH4MPJ S9S08SH4MPJ(auto trim)  
S9S08SH4MPJE S9S08SH4MPJE(auto trim)  
S9S08SH4MSC@SOIC8 [CX1030]  
S9S08SH4MSC@SOIC8(auto trim) [CX1030]  
S9S08SH4MSCE@SOIC8 [CX1030]  
S9S08SH4MSCE@SOIC8(auto trim) [CX1030]  
S9S08SH4MTG@TSSOP16 [CX1000]  
S9S08SH4MTG@TSSOP16(auto trim) [CX1000]  
S9S08SH4MTGE@TSSOP16 [CX1000]  
S9S08SH4MTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH4MTJ@TSSOP20 [CX1000]  
S9S08SH4MTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH4MTJE@TSSOP20 [CX1000]  
S9S08SH4MTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH4MWJ@SOIC20 [CX1033]  
S9S08SH4MWJ@SOIC20(auto trim) [CX1033]  
S9S08SH4MWJE@SOIC20 [CX1033]  
S9S08SH4MWJE@SOIC20(auto trim) [CX1033]  
S9S08SH4VFK@QFN24 [CX4012]  
S9S08SH4VFK@QFN24(auto trim) [CX4012]  
S9S08SH4VFKE@QFN24 [CX4012]  
S9S08SH4VFKE@QFN24(auto trim) [CX4012]  
S9S08SH4VPJ S9S08SH4VPJ(auto trim)  
S9S08SH4VPJE S9S08SH4VPJE(auto trim)  
S9S08SH4VSC@SOIC8 [CX1030]  
S9S08SH4VSC@SOIC8(auto trim) [CX1030]  
S9S08SH4VSCE@SOIC8 [CX1030]  
S9S08SH4VSCE@SOIC8(auto trim) [CX1030]  
S9S08SH4VTG@TSSOP16 [CX1000]  
S9S08SH4VTG@TSSOP16(auto trim) [CX1000]  
S9S08SH4VTGE@TSSOP16 [CX1000]  
S9S08SH4VTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH4VTJ@TSSOP20 [CX1000]  
S9S08SH4VTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH4VTJE@TSSOP20 [CX1000]  
S9S08SH4VTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH4VWJ@SOIC20 [CX1033]  
S9S08SH4VWJ@SOIC20(auto trim) [CX1033]  
S9S08SH4VWJE@SOIC20 [CX1033]  
S9S08SH4VWJE@SOIC20(auto trim) [CX1033]  
S9S08SH8CFK@QFN24 [CX4012]  
S9S08SH8CFK@QFN24(auto trim) [CX4012]  
S9S08SH8CFKE@QFN24 [CX4012]  
S9S08SH8CFKE@QFN24(auto trim) [CX4012]  
S9S08SH8CPJ S9S08SH8CPJ(auto trim)  
S9S08SH8CPJE S9S08SH8CPJE(auto trim)  
S9S08SH8CSC@SOIC8 [CX1030]  
S9S08SH8CSC@SOIC8(auto trim) [CX1030]  
S9S08SH8CSCE@SOIC8 [CX1030]  
S9S08SH8CSCE@SOIC8(auto trim) [CX1030]  
S9S08SH8CTG@TSSOP16 [CX1000]  
S9S08SH8CTG@TSSOP16(auto trim) [CX1000]  
S9S08SH8CTGE@TSSOP16 [CX1000]  
S9S08SH8CTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH8CTJ@TSSOP20 [CX1000]  
S9S08SH8CTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH8CTJE@TSSOP20 [CX1000]  
S9S08SH8CTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH8CWJ@SOIC20 [CX1033]

S9S08SH8CWJ@SOIC20(auto trim) [CX1033]  
S9S08SH8CWJE@SOIC20 [CX1033]  
S9S08SH8CWJE@SOIC20(auto trim) [CX1033]  
S9S08SH8MFK@QFN24 [CX4012]  
S9S08SH8MFK@QFN24(auto trim) [CX4012]  
S9S08SH8MFKE@QFN24 [CX4012]  
S9S08SH8MFKE@QFN24(auto trim) [CX4012]  
S9S08SH8MPJ S9S08SH8MPJ(auto trim)  
S9S08SH8MPJE S9S08SH8MPJE(auto trim)  
S9S08SH8MSC@SOIC8 [CX1030]  
S9S08SH8MSC@SOIC8(auto trim) [CX1030]  
S9S08SH8MSCE@SOIC8 [CX1030]  
S9S08SH8MSCE@SOIC8(auto trim) [CX1030]  
S9S08SH8MTG@TSSOP16 [CX1000]  
S9S08SH8MTG@TSSOP16(auto trim) [CX1000]  
S9S08SH8MTGE@TSSOP16 [CX1000]  
S9S08SH8MTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH8MTJ@TSSOP20 [CX1000]  
S9S08SH8MTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH8MTJE@TSSOP20 [CX1000]  
S9S08SH8MTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH8MWJ@SOIC20 [CX1033] S9S08SH8MWJE@SOIC20 [CX1033]  
S9S08SH8MWJE@SOIC20(auto trim) [CX1033]  
S9S08SH8VFK@QFN24 [CX4012]  
S9S08SH8VFK@QFN24(auto trim) [CX4012]  
S9S08SH8VFKE@QFN24 [CX4012]  
S9S08SH8VFKE@QFN24(auto trim) [CX4012]  
S9S08SH8VPJ S9S08SH8VPJ(auto trim)  
S9S08SH8VPJE S9S08SH8VPJE(auto trim)  
S9S08SH8VSC@SOIC8 [CX1030]  
S9S08SH8VSC@SOIC8(auto trim) [CX1030]  
S9S08SH8VSCE@SOIC8 [CX1030]  
S9S08SH8VSCE@SOIC8(auto trim) [CX1030]  
S9S08SH8VTG@TSSOP16 [CX1000]  
S9S08SH8VTG@TSSOP16(auto trim) [CX1000]  
S9S08SH8VTGE@TSSOP16 [CX1000]  
S9S08SH8VTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH8VTJ@TSSOP20 [CX1000]  
S9S08SH8VTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH8VTJE@TSSOP20 [CX1000]  
S9S08SH8VTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH8VWJ@SOIC20 [CX1033]  
S9S08SH8VWJ@SOIC20(auto trim) [CX1033]  
S9S08SH8VWJE@SOIC20 [CX1033]  
S9S08SH8VWJE@SOIC20(auto trim) [CX1033]  
S9S08SH9MWJ@SOIC20(auto trim) [CX1033]  
SC101161DGC@TQFP80 [CX3018] SC101161DGM@TQFP80 [CX3018]  
SC101161DGV@TQFP80 [CX3018] SC101161DJCFU@TQFP80 [CX3018]  
SC101161DJM@TQFP80 [CX3018] SC101161DJVFU@TQFP80 [CX3018]  
SC101161DTC@TQFP80 [CX3018] SC101161DTMFU@TQFP80 [CX3018]  
SC101161DTV@TQFP80 [CX3018] SC102202CFU@TQFP80 [CX3018]  
SC102202MFU@TQFP80 [CX3018] SC102202VFU@TQFP80 [CX3018]  
SC102203CFU@TQFP80 [CX3018] SC102203MFU@TQFP80 [CX3018]  
SC102203VFU@TQFP80 [CX3018] SC102204CFU@TQFP80 [CX3018]  
SC102204MFU@TQFP80 [CX3018] SC102204VFU@TQFP80 [CX3018]  
SC102205CFU@TQFP80 [CX3018] SC102205MFU@TQFP80 [CX3018]  
SC102205VFU@TQFP80 [CX3018] SC515846CFU@TQFP80 [CX3018]  
SC515846MFU@TQFP80 [CX3018] SC515846VFU@TQFP80 [CX3018]  
SC515847CFU@TQFP80 [CX3018] SC515847MFU@TQFP80 [CX3018]



SC515847VFU@TQFP80 [CX3018]  
SC515848MFU@TQFP80 [CX3018]  
SC515849CFU@TQFP80 [CX3018]  
SC515849VFU@TQFP80 [CX3018]  
XC68HC705P6A(CDW)@SOIC28 [CX1033]  
XC68HSC705C9A [CX0001]  
XC68HSC705C9A@TQFP44 [CX3002]

SC515848CFU@TQFP80 [CX3018]  
SC515848VFU@TQFP80 [CX3018]  
SC515849MFU@TQFP80 [CX3018]  
XC68HSC705C9A@PLCC44 [CX2044]

## Fremont Micro Devices

### E (E) PROM/FRAM/NVRAM

FT24C02 [CX0001]  
FT24C02@TSSOP8 [CX1059]  
FT24C02A@SOP8 [CX1045]  
FT24C04 [CX0001]  
FT24C04@TSSOP8 [CX1059]  
FT24C04A@SOP8 [CX1045]  
FT24C08 [CX0001]  
FT24C08@TSSOP8 [CX1059]  
FT24C08A@SOP8 [CX1045]  
FT24C128 [CX0001]  
FT24C128@TSSOP8 [CX1059]  
FT24C128A@SOP8 [CX1045]  
FT24C16 [CX0001]  
FT24C16@TSSOP8 [CX1059]  
FT24C16A@SOP8 [CX1045]  
FT24C256 [CX0001]  
FT24C256@TSSOP8 [CX1059]  
FT24C256A@SOP8 [CX1045]  
FT24C32 [CX0001]  
FT24C32@TSSOP8 [CX1059]  
FT24C32A@SOP8 [CX1045]  
FT24C512A [CX0001]  
FT24C512A@TSSOP8 [CX1059]  
FT24C64@SOP8 [CX1045]  
FT24C64A [CX0001]  
FT24C64A@TSSOP8 [CX1059]  
FT25C016@SOIC8 [CX1045]  
FT25C016A [CX0001]  
FT25C016A@TSSOP8 [CX1059]  
FT25C064@SOIC8 [CX1045]  
FT25C064A [CX0001]  
FT25C064A@TSSOP8 [CX1059]  
FT34C02@SOP8 [CX1045]  
FT34C02A [CX0001]  
FT34C02A@TSSOP8 [CX1059]  
FT93C46(08bit)@SOP8 [CX1045]  
FT93C46(16bit) [CX0001]  
FT93C46(16bit)@TSSOP8 [CX1059]  
FT93C46A(08bit)@SOP8 [CX1045]  
FT93C46A(16bit) [CX0001]  
FT93C46A(16bit)@TSSOP8 [CX1059]  
FT93C56(08bit)@SOP8 [CX1045]  
FT93C56(16bit) [CX0001]  
FT93C56(16bit)@TSSOP8 [CX1059]  
FT93C56A(08bit)@SOP8 [CX1045]  
FT93C56A(16bit) [CX0001]

FT24C02@SOP8 [CX1045]  
FT24C02A [CX0001]  
FT24C02A@TSSOP8 [CX1059]  
FT24C04@SOP8 [CX1045]  
FT24C04A [CX0001]  
FT24C04A@TSSOP8 [CX1059]  
FT24C08@SOP8 [CX1045]  
FT24C08A [CX0001]  
FT24C08A@TSSOP8 [CX1059]  
FT24C128@SOP8 [CX1045]  
FT24C128A [CX0001]  
FT24C128A@TSSOP8 [CX1059]  
FT24C16@SOP8 [CX1045]  
FT24C16A [CX0001]  
FT24C16A@TSSOP8 [CX1059]  
FT24C256@SOP8 [CX1045]  
FT24C256A [CX0001]  
FT24C256A@TSSOP8 [CX1059]  
FT24C32@SOP8 [CX1045]  
FT24C32A [CX0001]  
FT24C32A@TSSOP8 [CX1059]  
FT24C512A@SOP8 [CX1045]  
FT24C64 [CX0001]  
FT24C64@TSSOP8 [CX1059]  
FT24C64A@SOP8 [CX1045]  
FT25C016 [CX0001]  
FT25C016@TSSOP8 [CX1059]  
FT25C016A@SOIC8 [CX1045]  
FT25C064 [CX0001]  
FT25C064@TSSOP8 [CX1059]  
FT25C064A@SOIC8 [CX1045]  
FT34C02 [CX0001]  
FT34C02@TSSOP8 [CX1059]  
FT34C02A@SOP8 [CX1045]  
FT93C46(08bit) [CX0001]  
FT93C46(08bit)@TSSOP8 [CX1059]  
FT93C46(16bit)@SOP8 [CX1045]  
FT93C46A(08bit) [CX0001]  
FT93C46A(08bit)@TSSOP8 [CX1059]  
FT93C46A(16bit)@SOP8 [CX1045]  
FT93C56(08bit) [CX0001]  
FT93C56(08bit)@TSSOP8 [CX1059]  
FT93C56(16bit)@SOP8 [CX1045]  
FT93C56A(08bit) [CX0001]  
FT93C56A(08bit)@TSSOP8 [CX1059]  
FT93C56A(16bit)@SOP8 [CX1045]

FT93C56A(16bit)@TSSOP8 [CX1059]  
FT93C66(08bit)@SOIC8 [CX1045]  
FT93C66(16bit) [CX0001]  
FT93C66(16bit)@TSSOP8 [CX1059]  
FT93C66A(08bit)@SOP8 [CX1045]  
FT93C66A(16bit) [CX0001]  
FT93C66A(16bit)@TSSOP8 [CX1059]  
FT93C86(08bit)@SOP8 [CX1045]  
FT93C86(16bit) [CX0001]  
FT93C86(16bit)@TSSOP8 [CX1059]  
FT93C86A(08bit)@SOP8 [CX1045]  
FT93C86A(16bit) [CX0001]  
FT93C86A(16bit)@TSSOP8 [CX1059]

FT93C66(08bit) [CX0001]  
FT93C66(08bit)@TSSOP8 [CX1059]  
FT93C66(16bit)@SOP8 [CX1045]  
FT93C66A(08bit) [CX0001]  
FT93C66A(08bit)@TSSOP8 [CX1059]  
FT93C66A(16bit)@SOP8 [CX1045]  
FT93C86(08bit) [CX0001]  
FT93C86(08bit)@TSSOP8 [CX1059]  
FT93C86(16bit)@SOP8 [CX1045]  
FT93C86A(08bit) [CX0001]  
FT93C86A(08bit)@TSSOP8 [CX1059]  
FT93C86A(16bit)@SOP8 [CX1045]

## FTDICHIP

### MICROCONTROLLER

VNC1L [CX3007-4]  
VNC2-48L1B [CX3007-4]  
VNC2L-48L1B [CX3007-4]

VNC2-32L1B [CX3001]  
VNC2L-32L1B [CX3001]

## FUDAN

### E(E) PROM/FRAM/NVRAM

FM24C02A [CX0001]  
FM24C02A@TSSOP8 [CX1059]  
FM24C02B@SOIC8 [CX1045]  
FM24C02C [CX0001]  
FM24C02C@TSSOP8 [CX1059]  
FM24C04A@SOP8 [CX1045]  
FM24C04B [CX0001]  
FM24C04B@TSSOP8 [CX1059]  
FM24C08A@SOP8 [CX1045]  
FM24C08B [CX0001]  
FM24C08B@SOIC8 [CX1045]  
FM24C1024A [CX0001]  
FM24C1024A@TSSOP8 [CX1059]  
FM24C128A@MSOP8 [CX1015]  
FM24C128A@TDFN8 [CX4002]  
FM24C16A [CX0001]  
FM24C16A@TSSOP8 [CX1059]  
FM24C16B@SOIC8 [CX1045]  
FM24C256A [CX0001]  
FM24C256A@SOP8 [CX1045]  
FM24C256A@TSSOP8 [CX1059]  
FM24C32A@SOIC8 [CX1045]  
FM24C512A [CX0001]  
FM24C512A@TSSOP8 [CX1059]  
FM24C64A@SOIC8 [CX1045]  
FM25F005@SOP8 [CX1045#1]  
FM25F005@TSSOP8 [CX1059#1]  
FM25F01@TDFN8 [CX4002#1]  
FM25F02@SOP8(150 mil) [CX1045#1]  
FM25F02@TDFN8 [CX4005#1]  
FM25F02A@SOP8(150 mil) [CX1045#1]

FM24C02A@SOIC8 [CX1045]  
FM24C02B [CX0001]  
FM24C02B@TSSOP8 [CX1059]  
FM24C02C@SOP8 [CX1045]  
FM24C04A [CX0001]  
FM24C04A@TSSOP8 [CX1059]  
FM24C04B@SOIC8 [CX1045]  
FM24C08A [CX0001]  
FM24C08A@TSSOP8 [CX1059]  
FM24C08B(ISP) [CX0001]  
FM24C08B@TSSOP8 [CX1059]  
FM24C1024A@SOP8 [CX1045]  
FM24C128A [CX0001]  
FM24C128A@SOP8 [CX1045]  
FM24C128A@TSSOP8 [CX1059]  
FM24C16A@SOIC8 [CX1045]  
FM24C16B [CX0001]  
FM24C16B@TSSOP8 [CX1059]  
FM24C256A@MSOP8 [CX1015]  
FM24C256A@TDFN8 [CX4002]  
FM24C32A [CX0001]  
FM24C32A@TSSOP8 [CX1059]  
FM24C512A@SOP8 [CX1045]  
FM24C64A [CX0001]  
FM24C64A@TSSOP8 [CX1059]  
FM25F005@TDFN8 [CX4002#1]  
FM25F01@SOP8 [CX1045#1]  
FM25F01@TSSOP8 [CX1059#1]  
FM25F02@SOP8(208 mil) [CX1044#1]

FM25F02A@SOP8(208 mil) [CX1044#1]  
FM25F02A@TDFN8 [CX4005#1]  
FM25F04@SOP8(208 mil) [CX1044#1]  
FM25F04A@SOP8(150 mil) [CX1045#1]  
FM25F04A@SOP8(208 mil) [CX1044#1]  
FM25F04A@TDFN8 [CX4005#1]  
FM25Q32@SOP8(208 mil) [CX1044#1]  
FM93C46(08bit) [CX0001]  
FM93C46(08bit)@TDFN8 [CX4002]  
FM93C46(08bit)@TSOT23-6L [CX1041]  
FM93C46(08bit)@TSSOP8 [CX1059]  
FM93C46(16bit)@SOP8 [CX1045]  
FM93C46(16bit)@TSOT23-6L [CX1041]  
FM93C46(16bit)@TSSOP8 [CX1059]  
FM93C56(08bit)@SOP8 [CX1045]  
FM93C56(08bit)@TSOT23-6L [CX1041]  
FM93C56(08bit)@TSSOP8 [CX1059]  
FM93C56(16bit)@SOP8 [CX1045]  
FM93C56(16bit)@TSOT23-6L [CX1041]  
FM93C56(16bit)@TSSOP8 [CX1059]  
FM93C66(08bit)@SOP8 [CX1045]  
FM93C66(08bit)@TSOT23-6L [CX1041]  
FM93C66(08bit)@TSSOP8 [CX1059]  
FM93C66(16bit)@SOP8 [CX1045]  
FM93C66(16bit)@TSOT23-6L [CX1041]  
FM93C66(16bit)@TSSOP8 [CX1059]

FM25F04@SOP8(150 mil) [CX1045#1]  
FM25F04@TDFN8 [CX4005#1]  
FM25Q32@SOP8(150 mil) [CX1045#1]  
FM25Q32@TDFN8 [CX4005#1]  
FM93C46(08bit)@SOP8 [CX1045]  
FM93C46(16bit) [CX0001]  
FM93C46(16bit)@TDFN8 [CX4002]  
FM93C56(08bit) [CX0001]  
FM93C56(08bit)@TDFN8 [CX4002]  
FM93C56(16bit) [CX0001]  
FM93C56(16bit)@TDFN8 [CX4002]  
FM93C66(08bit) [CX0001]  
FM93C66(08bit)@TDFN8 [CX4002]  
FM93C66(16bit) [CX0001]  
FM93C66(16bit)@TDFN8 [CX4002]

## FUJITSU

### E (E) PROM/FRAM/NVRAM

MB84VD21081@FBGA61 [CX5048]  
MB84VD21081EM@FBGA56 [CX5045]  
MB84VD21082EA@FBGA56 [CX5045]  
MB84VD21083@FBGA61 [CX5048]  
MB84VD21083EM@FBGA56 [CX5045]  
MB84VD21084EA@FBGA56 [CX5045]  
MB84VD21091@FBGA61 [CX5048]  
MB84VD21091EM@FBGA56 [CX5045]  
MB84VD21092EA@FBGA56 [CX5045]  
MB84VD21093@FBGA61 [CX5048]  
MB84VD21093EM@FBGA56 [CX5045]  
MB84VD21094EA@FBGA56 [CX5045]  
MB84VD21181DA@FBGA69 [CX5001]  
MB84VD21181EM@FBGA56 [CX5045]  
MB84VD21182EG@FBGA56 [CX5045]  
MB84VD21183DA@FBGA69 [CX5001]  
MB84VD21183EM@FBGA56 [CX5045]  
MB84VD21184EG@FBGA56 [CX5045]  
MB84VD21191DA@FBGA69 [CX5001]  
MB84VD21191EM@FBGA56 [CX5045]  
MB84VD21192EG@FBGA56 [CX5045]  
MB84VD21193DA@FBGA69 [CX5001]  
MB84VD21193EM@FBGA56 [CX5045]  
MB84VD21194EG@FBGA56 [CX5045]  
MB84VD22180FA@FBGA59 [CX5045]  
MB84VD22181EB@FBGA73 [CX5001]  
MB84VD22181EE@FBGA73 [CX5001]

MB84VD21081EA@FBGA56 [CX5045]  
MB84VD21082@FBGA61 [CX5048]  
MB84VD21082EM@FBGA56 [CX5045]  
MB84VD21083EA@FBGA56 [CX5045]  
MB84VD21084@FBGA61 [CX5048]  
MB84VD21084EM@FBGA56 [CX5045]  
MB84VD21091EA@FBGA56 [CX5045]  
MB84VD21092@FBGA61 [CX5048]  
MB84VD21092EM@FBGA56 [CX5045]  
MB84VD21093EA@FBGA56 [CX5045]  
MB84VD21094@FBGA61 [CX5048]  
MB84VD21094EM@FBGA56 [CX5045]  
MB84VD21181EG@FBGA56 [CX5045]  
MB84VD21182DA@FBGA69 [CX5001]  
MB84VD21182EM@FBGA56 [CX5045]  
MB84VD21183EG@FBGA56 [CX5045]  
MB84VD21184DA@FBGA69 [CX5001]  
MB84VD21184EM@FBGA56 [CX5045]  
MB84VD21191EG@FBGA56 [CX5045]  
MB84VD21192DA@FBGA69 [CX5001]  
MB84VD21192EM@FBGA56 [CX5045]  
MB84VD21193EG@FBGA56 [CX5045]  
MB84VD21194DA@FBGA69 [CX5001]  
MB84VD21194EM@FBGA56 [CX5045]  
MB84VD22180FM@FBGA59 [CX5045]  
MB84VD22181EC@FBGA73 [CX5001]  
MB84VD22181FM@FBGA56 [CX5045]

MB84VD22182EB@FBGA73 [CX5001]  
MB84VD22182EE@FBGA73 [CX5001]  
MB84VD22183EC@FBGA73 [CX5001]  
MB84VD22184EB@FBGA73 [CX5001]  
MB84VD22184EE@FBGA73 [CX5001]  
MB84VD22190FA@FBGA59 [CX5045]  
MB84VD22191EB@FBGA73 [CX5001]  
MB84VD22191EE@FBGA73 [CX5001]  
MB84VD22192EB@FBGA73 [CX5001]  
MB84VD22192EE@FBGA73 [CX5001]  
MB84VD22193EC@FBGA73 [CX5001]  
MB84VD22194EB@FBGA73 [CX5001]  
MB84VD22194EE@FBGA73 [CX5001]  
MB84VD22280FA@FBGA59 [CX5045]  
MB84VD22282EA@FBGA71 [CX5001]  
MB84VD22283EA@FBGA71 [CX5001]  
MB84VD22284EA@FBGA71 [CX5001]  
MB84VD22290FA@FBGA59 [CX5045]  
MB84VD22292EA@FBGA71 [CX5001]  
MB84VD22293EA@FBGA71 [CX5001]  
MB84VD22294EA@FBGA71 [CX5001]  
MB84VD22386EJ@FBGA71 [CX5001]  
MB84VD22388EJ@FBGA71 [CX5001]  
MB84VD22397EJ@FBGA71 [CX5001]  
MB84VD23180FM@FBGA73 [CX5001]  
MB84VD23381FJ@FBGA65 [CX5048]  
MB84VD23481FJ@FBGA65 [CX5048]  
MB84VP23481FK@FBGA65 [CX5048]  
MB84VP24491HK@FBGA73 [CX5001]  
MB85R256@TSOP28 [CX1001]  
MB85R256A@TSOP28 [CX1001]  
MB85RC128@SOIC8 [CX1045]  
MB85RC16@SOIC8 [CX1045]  
MB85RC64@SOIC8 [CX1045]  
MBM271001 [CX0001]  
MBM271001@TSOP32 [CX1002]  
MBM27128@PLCC32 [CX2032]  
MBM2716H [CX0001]  
MBM27256@PLCC32 [CX2032]  
MBM2732A [CX0001]  
MBM2764@PLCC32 [CX2032]  
MBM27C1000@PLCC32 [CX2032]  
MBM27C1001 [CX0001]  
MBM27C1001@TSOP32 [CX1002]  
MBM27C1024@PLCC44 [CX2044]  
MBM27C128@PLCC32 [CX2032]  
MBM27C128P@PLCC32 [CX2032]  
MBM27C2000@PLCC32 [CX2032]  
MBM27C2001 [CX0001]  
MBM27C2001@TSOP32 [CX1002]  
MBM27C256 [CX0001]  
MBM27C256A [CX0001]  
MBM27C256AP [CX0001]  
MBM27C256H [CX0001]  
MBM27C32A [CX0001]  
MBM27C4001@PLCC32 [CX2032]  
MBM27C4096 [CX0001]  
MBM27C512@PLCC32 [CX2032]  
MBM27C512P@PLCC32 [CX2032]

MB84VD22182EC@FBGA73 [CX5001]  
MB84VD22183EB@FBGA73 [CX5001]  
MB84VD22183EE@FBGA73 [CX5001]  
MB84VD22184EC@FBGA73 [CX5001]  
MB84VD22184FM@FBGA56 [CX5045]  
MB84VD22190FM@FBGA59 [CX5045]  
MB84VD22191EC@FBGA73 [CX5001]  
MB84VD22191FM@FBGA56 [CX5045]  
MB84VD22192EC@FBGA73 [CX5001]  
MB84VD22193EB@FBGA73 [CX5001]  
MB84VD22193EE@FBGA73 [CX5001]  
MB84VD22194EC@FBGA73 [CX5001]  
MB84VD22194FM@FBGA56 [CX5045]  
MB84VD22280FE@FBGA59 [CX5045]  
MB84VD22282EE@FBGA71 [CX5001]  
MB84VD22283EE@FBGA71 [CX5001]  
MB84VD22284EE@FBGA71 [CX5001]  
MB84VD22290FE@FBGA59 [CX5045]  
MB84VD22292EE@FBGA71 [CX5001]  
MB84VD22293EE@FBGA71 [CX5001]  
MB84VD22294EE@FBGA71 [CX5001]  
MB84VD22387EJ@FBGA71 [CX5001]  
MB84VD22396EJ@FBGA71 [CX5001]  
MB84VD22398EJ@FBGA71 [CX5001]  
MB84VD23280FA@FBGA65 [CX5048]  
MB84VD23381HJ@FBGA56 [CX5045]  
MB84VD23581FJ@FBGA65 [CX5048]  
MB84VP24481HK@FBGA73 [CX5001]  
MB85R256@SOP28 [CX1035]  
MB85R256A@SOP28 [CX1035]  
MB85RC128 [CX0001]  
MB85RC16 [CX0001]  
MB85RC64 [CX0001]  
MBM2212 [CX0001]  
MBM271001@PLCC32 [CX2032]  
MBM27128 [CX0001]  
MBM2716 [CX0001]  
MBM27256 [CX0001]  
MBM2732 [CX0001]  
MBM2764 [CX0001]  
MBM27C1000 [CX0001]  
MBM27C1000@TSOP32 [CX1002]  
MBM27C1001@PLCC32 [CX2032]  
MBM27C1024 [CX0001]  
MBM27C128 [CX0001]  
MBM27C128P [CX0001]  
MBM27C2000 [CX0001]  
MBM27C2000@TSOP32 [CX1002]  
MBM27C2001@PLCC32 [CX2032]  
MBM27C2048 [CX0001]  
MBM27C256@PLCC32 [CX2032]  
MBM27C256A@PLCC32 [CX2032]  
MBM27C256AP@PLCC32 [CX2032]  
MBM27C256H@PLCC32 [CX2032]  
MBM27C4001 [CX0001]  
MBM27C4001@TSOP32 [CX1002]  
MBM27C512 [CX0001]  
MBM27C512P [CX0001]  
MBM27C64 [CX0001]

MBM27C64@PLCC32 [CX2032] MBM28C64 [CX0001]  
MBM28C65 [CX0001] MBM28F010 [CX0001]  
MBM28F010(REVERSE)@TSOP32 [CX1002]  
MBM28F010@PLCC32 [CX2032] MBM28F010@SOP32 [CX1019]  
MBM28F010@TSOP32 [CX1002]  
MBM29DL161BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL161BD@FBGA48 [CX5002] MBM29DL161BD@TSOP48 [CX1004]  
MBM29DL161BE(REVERSE)@TSOP48 [CX1004]  
MBM29DL161BE@FBGA48 [CX5002] MBM29DL161BE@TSOP48 [CX1004]  
MBM29DL161TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL161TD@FBGA48 [CX5002] MBM29DL161TD@TSOP48 [CX1004]  
MBM29DL161TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL161TE@FBGA48 [CX5002] MBM29DL161TE@TSOP48 [CX1004]  
MBM29DL162BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL162BD@FBGA48 [CX5002] MBM29DL162BD@TSOP48 [CX1004]  
MBM29DL162BE(REVERSE)@TSOP48 [CX1004]  
MBM29DL162BE@FBGA48 [CX5002] MBM29DL162BE@TSOP48 [CX1004]  
MBM29DL162TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL162TD@FBGA48 [CX5002] MBM29DL162TD@TSOP48 [CX1004]  
MBM29DL162TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL162TE@FBGA48 [CX5002] MBM29DL162TE@TSOP48 [CX1004]  
MBM29DL163BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL163BD@FBGA48 [CX5002] MBM29DL163BD@TSOP48 [CX1004]  
MBM29DL163BE(REVERSE)@TSOP48 [CX1004]  
MBM29DL163BE@FBGA48 [CX5002] MBM29DL163BE@TSOP48 [CX1004]  
MBM29DL163TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL163TD@FBGA48 [CX5002] MBM29DL163TD@TSOP48 [CX1004]  
MBM29DL163TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL163TE@FBGA48 [CX5002] MBM29DL163TE@TSOP48 [CX1004]  
MBM29DL164BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL164BD@FBGA48 [CX5002] MBM29DL164BD@TSOP48 [CX1004]  
MBM29DL164BE(REVERSE)@TSOP48 [CX1004]  
MBM29DL164BE@FBGA48 [CX5002] MBM29DL164BE@TSOP48 [CX1004]  
MBM29DL164TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL164TD@FBGA48 [CX5002] MBM29DL164TD@TSOP48 [CX1004]  
MBM29DL164TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL164TE@FBGA48 [CX5002] MBM29DL164TE@TSOP48 [CX1004]  
MBM29DL320BF@FBGA48 [CX5039] MBM29DL320BF@TSOP48 [CX1004]  
MBM29DL320TF@FBGA48 [CX5039] MBM29DL320TF@TSOP48 [CX1004]  
MBM29DL321BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL321BD@FBGA63 [CX5047] MBM29DL321BD@TSOP48 [CX1004]  
MBM29DL321BE@FBGA63 [CX5047] MBM29DL321BE@TSOP48 [CX1004]  
MBM29DL321TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL321TD@FBGA63 [CX5047] MBM29DL321TD@TSOP48 [CX1004]  
MBM29DL321TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL321TE@FBGA63 [CX5047] MBM29DL321TE@TSOP48 [CX1004]  
MBM29DL322BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL322BD@FBGA63 [CX5047] MBM29DL322BD@TSOP48 [CX1004]  
MBM29DL322BE(REVERSE)@TSOP48 [CX1004]  
MBM29DL322BE@FBGA63 [CX5047] MBM29DL322BE@TSOP48 [CX1004]  
MBM29DL322TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL322TD@FBGA63 [CX5047] MBM29DL322TD@TSOP48 [CX1004]  
MBM29DL322TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL322TE@FBGA63 [CX5047] MBM29DL322TE@TSOP48 [CX1004]  
MBM29DL323BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL323BD@FBGA63 [CX5047] MBM29DL323BD@TSOP48 [CX1004]  
MBM29DL323BE(REVERSE)@TSOP48 [CX1004]  
MBM29DL323BE@FBGA63 [CX5047] MBM29DL323BE@TSOP48 [CX1004]  
MBM29DL323BF@FBGA48 [CX5039] MBM29DL323BF@TSOP48 [CX1004]

MBM29DL323TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL323TD@FBGA63 [CX5047] MBM29DL323TD@TSOP48 [CX1004]  
MBM29DL323TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL323TE@FBGA63 [CX5047] MBM29DL323TE@TSOP48 [CX1004]  
MBM29DL323TF@FBGA48 [CX5039] MBM29DL323TF@TSOP48 [CX1004]  
MBM29DL324BD(REVERSE)@TSOP48 [CX1004]  
MBM29DL324BD@FBGA63 [CX5047] MBM29DL324BD@TSOP48 [CX1004]  
MBM29DL324BE(REVERSE)@TSOP48 [CX1004]  
MBM29DL324BE@FBGA63 [CX5047] MBM29DL324BE@TSOP48 [CX1004]  
MBM29DL324TD(REVERSE)@TSOP48 [CX1004]  
MBM29DL324TD@FBGA63 [CX5047] MBM29DL324TD@TSOP48 [CX1004]  
MBM29DL324TE(REVERSE)@TSOP48 [CX1004]  
MBM29DL324TE@FBGA63 [CX5047] MBM29DL324TE@TSOP48 [CX1004]  
MBM29DL32BF@FBGA48 [CX5039] MBM29DL32BF@TSOP48 [CX1004]  
MBM29DL32TF@FBGA48 [CX5039] MBM29DL32TF@TSOP48 [CX1004]  
MBM29DL34BF@FBGA48 [CX5039] MBM29DL34BF@TSOP48 [CX1004]  
MBM29DL34TF@FBGA48 [CX5039] MBM29DL34TF@TSOP48 [CX1004]  
MBM29DL400BB@PSOP44 [CX1014] MBM29DL400BB@TSOP48 [CX1004]  
MBM29DL400BC(REVERSE)@TSOP48 [CX1004]  
MBM29DL400BC@PSOP44 [CX1014] MBM29DL400BC@TSOP48 [CX1004]  
MBM29DL400BT@PSOP44 [CX1014] MBM29DL400BT@TSOP48 [CX1004]  
MBM29DL400TC(REVERSE)@TSOP48 [CX1004]  
MBM29DL400TC@PSOP44 [CX1014] MBM29DL400TC@TSOP48 [CX1004]  
MBM29DL640E(REVERSE)@TSOP48 [CX1004]  
MBM29DL640E@FBGA63 [CX5041] MBM29DL640E@TSOP48 [CX1004]  
MBM29DL64DF@FBGA48 [CX5022] MBM29DL64DF@TSOP48 [CX1004]  
MBM29DL800B@PSOP44 [CX1014] MBM29DL800B@TSOP48 [CX1004]  
MBM29DL800BA(REVERSE)@TSOP48 [CX1004]  
MBM29DL800BA@FBGA48 [CX5039] MBM29DL800BA@PSOP44 [CX1014]  
MBM29DL800BA@TSOP48 [CX1004] MBM29DL800BB@PSOP44 [CX1014]  
MBM29DL800BB@TSOP48 [CX1004] MBM29DL800BT@PSOP44 [CX1014]  
MBM29DL800BT@TSOP48 [CX1004] MBM29DL800T@PSOP44 [CX1014]  
MBM29DL800T@TSOP48 [CX1004]  
MBM29DL800TA(REVERSE)@TSOP48 [CX1004]  
MBM29DL800TA@FBGA48 [CX5039] MBM29DL800TA@PSOP44 [CX1014]  
MBM29DL800TA@TSOP48 [CX1004] MBM29DS163BE@FBGA48 [CX5043]  
MBM29DS163BE@TSOP48 [CX1004] MBM29DS163TE@FBGA48 [CX5043]  
MBM29DS163TE@TSOP48 [CX1004] MBM29F001B [CX0001]  
MBM29F001B@PLCC32 [CX2032] MBM29F001B@TSOP32 [CX1002]  
MBM29F001T [CX0001] MBM29F001T@PLCC32 [CX2032]  
MBM29F001T@TSOP32 [CX1002] MBM29F002B [CX0001]  
MBM29F002B@PLCC32 [CX2032] MBM29F002B@TSOP32 [CX1002]  
MBM29F002NB [CX0001] MBM29F002NB@PLCC32 [CX2032]  
MBM29F002NB@TSOP32 [CX1002] MBM29F002NT [CX0001]  
MBM29F002NT@PLCC32 [CX2032] MBM29F002NT@TSOP32 [CX1002]  
MBM29F002T [CX0001] MBM29F002T@PLCC32 [CX2032]  
MBM29F002T@TSOP32 [CX1002] MBM29F010 [CX0001]  
MBM29F010@PLCC32 [CX2032] MBM29F010@TSOP32 [CX1002]  
MBM29F010A [CX0001] MBM29F010A@PLCC32 [CX2032]  
MBM29F010A@TSOP32 [CX1002] MBM29F016@PSOP44 [CX1014]  
MBM29F016@TSOP40 [CX1006] MBM29F016@TSOP48 [CX1004]  
MBM29F016A@PSOP44 [CX1014] MBM29F016A@TSOP40 [CX1006]  
MBM29F016A@TSOP48 [CX1004] MBM29F016B@PSOP44 [CX1014]  
MBM29F016B@TSOP40 [CX1006] MBM29F016B@TSOP48 [CX1004]  
MBM29F017A(REVERSE)@TSOP48 [CX1004]  
MBM29F017A@TSOP48 [CX1004] MBM29F017B@TSOP48 [CX1004]  
MBM29F017D@TSOP40 [CX1006] MBM29F017D@TSOP48 [CX1004]  
MBM29F032B@PSOP44 [CX1014] MBM29F032B@TSOP40 [CX1006]  
MBM29F033C@TSOP40 [CX1006] MBM29F040 [CX0001]

MBM29F040@PLCC32 [CX2032] MBM29F040@TSOP32 [CX1002]  
MBM29F040B [CX0001] MBM29F040B@PLCC32 [CX2032]  
MBM29F040B@TSOP32 [CX1002] MBM29F040C@PLCC32 [CX2032]  
MBM29F040C@TSOP32 [CX1002] MBM29F080@PSOP44 [CX1014]  
MBM29F080@TSOP40 [CX1006]  
MBM29F080A(REVERSE)@TSOP40 [CX1006]  
MBM29F080A(REVERSE)@TSOP48 [CX1004]  
MBM29F080A@PSOP44 [CX1014] MBM29F080A@TSOP40 [CX1006]  
MBM29F080A@TSOP48 [CX1004] MBM29F080B@PSOP44 [CX1014]  
MBM29F080B@TSOP40 [CX1006] MBM29F100B@PSOP44 [CX1014]  
MBM29F100B@TSOP48 [CX1004] MBM29F100T@PSOP44 [CX1014]  
MBM29F100T@TSOP48 [CX1004]  
MBM29F160BE(REVERSE)@TSOP48 [CX1004]  
MBM29F160BE@TSOP48 [CX1004]  
MBM29F160TE(REVERSE)@TSOP48 [CX1004]  
MBM29F160TE@TSOP48 [CX1004]  
MBM29F160TE@TSOP48(slow) [CX1043]  
MBM29F200AB@PSOP44 [CX1014] MBM29F200AB@TSOP48 [CX1004]  
MBM29F200AT@PSOP44 [CX1014] MBM29F200AT@TSOP48 [CX1004]  
MBM29F200B@PSOP44 [CX1014] MBM29F200B@TSOP48 [CX1004]  
MBM29F200BC(REVERSE)@TSOP48 [CX1004]  
MBM29F200BC@PSOP44 [CX1014] MBM29F200BC@TSOP48 [CX1004]  
MBM29F200T@PSOP44 [CX1014] MBM29F200T@TSOP48 [CX1004]  
MBM29F200TC(REVERSE)@TSOP48 [CX1004]  
MBM29F200TC@PSOP44 [CX1014] MBM29F200TC@TSOP48 [CX1004]  
MBM29F400AB@PSOP44 [CX1014] MBM29F400AB@TSOP48 [CX1004]  
MBM29F400AT@PSOP44 [CX1014] MBM29F400AT@TSOP48 [CX1004]  
MBM29F400B@PSOP44 [CX1014] MBM29F400B@TSOP48 [CX1004]  
MBM29F400BB@PSOP44 [CX1014] MBM29F400BB@TSOP48 [CX1004]  
MBM29F400BC(REVERSE)@TSOP48 [CX1004]  
MBM29F400BC@PSOP44 [CX1014] MBM29F400BC@TSOP48 [CX1004]  
MBM29F400BT@PSOP44 [CX1014] MBM29F400BT@TSOP48 [CX1004]  
MBM29F400T@PSOP44 [CX1014] MBM29F400T@TSOP48 [CX1004]  
MBM29F400TC(REVERSE)@TSOP48 [CX1004]  
MBM29F400TC@PSOP44 [CX1014] MBM29F400TC@TSOP48 [CX1004]  
MBM29F800B@PSOP44 [CX1014] MBM29F800B@TSOP48 [CX1004]  
MBM29F800BA(REVERSE)@TSOP48 [CX1004]  
MBM29F800BA@PSOP44 [CX1014] MBM29F800BA@TSOP48 [CX1004]  
MBM29F800BB@PSOP44 [CX1014] MBM29F800BB@TSOP48 [CX1004]  
MBM29F800BT@PSOP44 [CX1014] MBM29F800BT@TSOP48 [CX1004]  
MBM29F800T@PSOP44 [CX1014] MBM29F800T@TSOP48 [CX1004]  
MBM29F800TA(REVERSE)@TSOP48 [CX1004]  
MBM29F800TA@PSOP44 [CX1014] MBM29F800TA@TSOP48 [CX1004]  
MBM29F800TA@TSOP48(slow) [CX1043]  
MBM29LL800B@TSOP48 [CX1004] MBM29LL800BB@TSOP48 [CX1004]  
MBM29LL800BT@TSOP48 [CX1004] MBM29LL800T@TSOP48 [CX1004]  
MBM29LV001B@PLCC32 [CX2032]  
MBM29LV001BB(REVERSE)@TSOP32 [CX1002]  
MBM29LV001BB@PLCC32 [CX2032] MBM29LV001BB@TSOP32 [CX1002]  
MBM29LV001BC(REVERSE)@TSOP32 [CX1002]  
MBM29LV001BC@PLCC32 [CX2032] MBM29LV001BC@TSOP32 [CX1002]  
MBM29LV001BT(REVERSE)@TSOP32 [CX1002]  
MBM29LV001BT@PLCC32 [CX2032] MBM29LV001BT@TSOP32 [CX1002]  
MBM29LV001T@TSOP32 [CX1002]  
MBM29LV001TC(REVERSE)@TSOP32 [CX1002]  
MBM29LV001TC@PLCC32 [CX2032] MBM29LV001TC@TSOP32 [CX1002]  
MBM29LV002B@TSOP40 [CX1006] MBM29LV002T@TSOP40 [CX1006]  
MBM29LV004B@TSOP40 [CX1006] MBM29LV004BB@TSOP40 [CX1006]  
MBM29LV004BT@TSOP40 [CX1006] MBM29LV004T@TSOP40 [CX1006]

MBM29LV008B@TSOP40 [CX1006] MBM29LV008BB@TSOP40 [CX1006]  
MBM29LV008BT@TSOP40 [CX1006] MBM29LV008T@TSOP40 [CX1006]  
MBM29LV016/B@TSOP40 [CX1006] MBM29LV016/T@TSOP40 [CX1006]  
MBM29LV016B@TSOP40 [CX1006] MBM29LV017@FBGA48 [CX5022]  
MBM29LV017@TSOP40 [CX1006] MBM29LV017B@TSOP40 [CX1006]  
MBM29LV017E@TSOP40 [CX1006] MBM29LV033C@TSOP40 [CX1006]  
MBM29LV080@TSOP40 [CX1006] MBM29LV080A@TSOP40 [CX1006]  
MBM29LV081@TSOP40 [CX1006] MBM29LV081B@TSOP40 [CX1006]  
MBM29LV116B@TSOP40 [CX1006]  
MBM29LV160B(REVERSE)@TSOP48 [CX1004]  
MBM29LV160B@FBGA48 [CX5022] MBM29LV160B@TSOP48 [CX1004]  
MBM29LV160BE(REVERSE)@TSOP48 [CX1004]  
MBM29LV160BE@FBGA48 [CX5002] MBM29LV160BE@PSOP44 [CX1014]  
MBM29LV160BE@TSOP48 [CX1004] MBM29LV160BM@FBGA48 [CX5002]  
MBM29LV160BM@TSOP48 [CX1004]  
MBM29LV160T(REVERSE)@TSOP48 [CX1004]  
MBM29LV160T@FBGA48 [CX5022] MBM29LV160T@TSOP48 [CX1004]  
MBM29LV160TE(REVERSE)@TSOP48 [CX1004]  
MBM29LV160TE@FBGA48 [CX5002] MBM29LV160TE@PSOP44 [CX1014]  
MBM29LV160TE@TSOP48 [CX1004] MBM29LV160TM@FBGA48 [CX5002]  
MBM29LV160TM@TSOP48 [CX1004] MBM29LV200B@PSOP44 [CX1014]  
MBM29LV200B@TSOP48 [CX1004] MBM29LV200BB@PSOP44 [CX1014]  
MBM29LV200BB@TSOP48 [CX1004]  
MBM29LV200BC(REVERSE)@TSOP48 [CX1004]  
MBM29LV200BC@PSOP44 [CX1014] MBM29LV200BC@TSOP48 [CX1004]  
MBM29LV200BT@PSOP44 [CX1014] MBM29LV200BT@TSOP48 [CX1004]  
MBM29LV200T@PSOP44 [CX1014] MBM29LV200T@TSOP48 [CX1004]  
MBM29LV200TC(REVERSE)@TSOP48 [CX1004]  
MBM29LV200TC@PSOP44 [CX1014] MBM29LV200TC@TSOP48 [CX1004]  
MBM29LV320BE(REVERSE)@TSOP48 [CX1004]  
MBM29LV320BE@FBGA63 [CX5063] MBM29LV320BE@TSOP48 [CX1004]  
MBM29LV320TE(REVERSE)@TSOP48 [CX1004]  
MBM29LV320TE@FBGA63 [CX5063] MBM29LV320TE@TSOP48 [CX1004]  
MBM29LV400B@PSOP44 [CX1014] MBM29LV400B@TSOP48 [CX1004]  
MBM29LV400BB@PSOP44 [CX1014] MBM29LV400BB@TSOP48 [CX1004]  
MBM29LV400BC@FBGA48 [CX5002] MBM29LV400BC@PSOP44 [CX1014]  
MBM29LV400BC@TSOP48 [CX1004] MBM29LV400BT@PSOP44 [CX1014]  
MBM29LV400BT@TSOP48 [CX1004] MBM29LV400T@PSOP44 [CX1014]  
MBM29LV400T@TSOP48 [CX1004] MBM29LV400TC@FBGA48 [CX5002]  
MBM29LV400TC@PSOP44 [CX1014] MBM29LV400TC@TSOP48 [CX1004]  
MBM29LV650UE(REVERSE)@TSOP48 [CX1004]  
MBM29LV650UE@TSOP48 [CX1004]  
MBM29LV651UE(REVERSE)@TSOP48 [CX1004]  
MBM29LV651UE@TSOP48 [CX1004] MBM29LV652UE@FBGA63 [CX5041]  
MBM29LV800B@PSOP44 [CX1014] MBM29LV800B@TSOP48 [CX1004]  
MBM29LV800BA(REVERSE)@TSOP48 [CX1004]  
MBM29LV800BA@FBGA48 [CX5039] MBM29LV800BA@PSOP44 [CX1014]  
MBM29LV800BA@TSOP48 [CX1004] MBM29LV800BB@PSOP44 [CX1014]  
MBM29LV800BB@TSOP48 [CX1004]  
MBM29LV800BE(REVERSE)@TSOP48 [CX1004]  
MBM29LV800BE@FBGA48 [CX5039] MBM29LV800BE@PSOP44 [CX1014]  
MBM29LV800BE@TSOP48 [CX1004] MBM29LV800BT@PSOP44 [CX1014]  
MBM29LV800BT@TSOP48 [CX1004] MBM29LV800T@PSOP44 [CX1014]  
MBM29LV800T@TSOP48 [CX1004]  
MBM29LV800TA(REVERSE)@TSOP48 [CX1004]  
MBM29LV800TA@FBGA48 [CX5039] MBM29LV800TA@PSOP44 [CX1014]  
MBM29LV800TA@TSOP48 [CX1004]  
MBM29LV800TE(REVERSE)@TSOP48 [CX1004]  
MBM29LV800TE@FBGA48 [CX5039] MBM29LV800TE@PSOP44 [CX1014]



MBM29LV800TE@TSOP48 [CX1004]	MBM29PDS323B@FBGA63 [CX5047]
MBM29PDS323T@FBGA63 [CX5047]	MBM29PL12LM@TSOP56 [CX1011]
MBM29PL160BD@PSOP44 [CX1014]	MBM29PL160BD@TSOP48 [CX1004]
MBM29PL160TD@PSOP44 [CX1014]	MBM29PL160TD@TSOP48 [CX1004]
MBM29PL32BM@FBGA48 [CX5002]	MBM29PL32BM@TSOP48 [CX1004]
MBM29PL32TM@FBGA48 [CX5002]	MBM29PL32TM@TSOP48 [CX1004]
MBM29PL64LM@TSOP48 [CX1004]	MBM29PL64LM@TSOP56 [CX1011]
MBM29PL65LM@TSOP48 [CX1004]	MBM29QM12DH@FBGA80 [CX5001]
MBM29QM12DH@TSOP56 [CX1011]	
MBM29SL160BD(REVERSE)@TSOP48 [CX1004]	
MBM29SL160BD@FBGA48 [CX5022]	MBM29SL160BD@TSOP48 [CX1004]
MBM29SL160TD(REVERSE)@TSOP48 [CX1004]	
MBM29SL160TD@FBGA48 [CX5022]	MBM29SL160TD@TSOP48 [CX1004]
MBM29SL800BD(REVERSE)@TSOP48 [CX1004]	
MBM29SL800BD@FBGA48 [CX5022]	MBM29SL800BD@TSOP48 [CX1004]
MBM29SL800BE@FBGA48 [CX5043]	
MBM29SL800TD(REVERSE)@TSOP48 [CX1004]	
MBM29SL800TD@FBGA48 [CX5002]	MBM29SL800TD@TSOP48 [CX1004]
MBM29SL800TE@FBGA48 [CX5043]	MSP29LV128@PSOP44 [CX1014]
MSP29LV128N@PSOP44 [CX1014]	MSP29LV256@TSOP56 [CX1057]
MSP29LV512@SSOP70 [CX1057]	MSP29LV512@TSOP56 [CX1057]
MSP55LV650@PSOP44(slow) [CX1014]	MSP64LV100@FBGA54 [CX5004]
MSP64LV200@FBGA54 [CX5004]	MSP64LV202@FBGA54 [CX5004]

#### DRAM & SRAM

MB81C78A [CX0001]	MB81C78A@SOIC28
-------------------	-----------------

#### MICROCONTROLLER

MB85RS256 [CX0001]	MB85RS256@SOIC14 [CX1033]
MB85RS256@SOIC8 [CX1045]	MB85RS256A [CX0001]
MB85RS256A@SOIC14 [CX1033]	MB85RS256A@SOIC8 [CX1045]
MB89F202@SDIP32 [CX0032]	MB89F202@SSOP34 [CX1027]
MB89F202A@SDIP32 [CX0032]	MB89F202A@SSOP34 [CX1027]
MB89F202R@QFP32 [CX3001]	MB89F202R@SDIP32 [CX0032]
MB89F202R@SSOP34 [CX1027]	MB89F202RA@QFP32 [CX3001]
MB89F202RA@SDIP32 [CX0032]	MB89F202RA@SSOP34 [CX1027]
MB89F482AS@LQFP44 [CX3002]	MB89F482AS@SDIP42 [CX0042]
MB89F482AW@LQFP44 [CX3002]	MB89F482AW@SDIP42 [CX0042]
MB89F482HS@LQFP44 [CX3002]	MB89F482HS@SDIP42 [CX0042]
MB89F482HW@LQFP44 [CX3002]	MB89F482HW@SDIP42 [CX0042]
MB89F497APF@QFP80 [CX3020]	MB89F497APFV@LQFP80 [CX3017]
MB89F497PF@QFP80 [CX3020]	MB89F497PFV@LQFP80 [CX3017]
MB89F499PF@QFP100 [CX3023]	MB89F499PFV@LQFP100 [CX3043]
MB89F538@SDIP64 [CX0064]	MB89F538-101PF@TQFP64 [CX3011]
MB89F538-101PFM@TQFP64 [CX3012]	MB89F538-201PF@TQFP64 [CX3011]
MB89F538-201PFM@TQFP64 [CX3012]	MB89F538L@SDIP64 [CX0064]
MB89F538L-101PF@TQFP64 [CX3011]	MB89F538L-101PFM@TQFP64 [CX3012]
MB89F538L-201PF@TQFP64 [CX3011]	MB89F538L-201PFM@TQFP64 [CX3012]
MB89P131APFM@QFP48 [CX3006]	MB89P131PFM@QFP48 [CX3006]
MB89P133APFM@QFP48 [CX3006]	MB89P133PFM@QFP48 [CX3006]
MB89P135APFM@QFP48 [CX3006]	MB89P135PFM@QFP48 [CX3006]
MB89P195 [CX0001]	MB89P195(F)@SOIC28 [CX1035]
MB89P195AP [CX0001]	MB89P195AP(F)@SOIC28 [CX1035]
MB89P195P [CX0001]	MB89P195P(F)@SOIC28 [CX1035]
MB89P475-101P-SH@SDIP48 [CX0048]	MB89P475-102P-SH@SDIP48 [CX0048]
MB89P475-201P-SH@SDIP48 [CX0048]	MB89P475-202P-SH@SDIP48 [CX0048]

MB89P485LPFM-101@TQFP64 [CX3012] MB89P485LPFM-102@TQFP64 [CX3012]  
MB89P485LPFM-103@TQFP64 [CX3012] MB89P485LPFM-104@TQFP64 [CX3012]  
MB89P485LPFV-101@TQFP64 [CX3011] MB89P485LPFV-102@TQFP64 [CX3011]  
MB89P485LPFV-103@TQFP64 [CX3011] MB89P485LPFV-104@TQFP64 [CX3011]  
MB89P485PFM-101@TQFP64 [CX3012] MB89P485PFM-102@TQFP64 [CX3012]  
MB89P485PFM-103@TQFP64 [CX3012] MB89P485PFM-104@TQFP64 [CX3012]  
MB89P485PFV-101@TQFP64 [CX3011] MB89P485PFV-102@TQFP64 [CX3011]  
MB89P485PFV-103@TQFP64 [CX3011] MB89P485PFV-104@TQFP64 [CX3011]  
MB89P538@LQFP64 [CX3064] MB89P538@PQFP64 [CX3049]  
MB89P538@SDIP64 [CX0064] MB89P538L@LQFP64 [CX3064]  
MB89P538L@PQFP64 [CX3049] MB89P538L@SDIP64 [CX0064]  
MB89P627@LQFP64 [CX3011] MB89P627@QFP64 [CX3015]  
MB89P627@SDIP64 [CX0064] MB89P627@TQFP64 [CX3064]  
MB89P627P@LQFP64 [CX3011] MB89P627P@QFP64 [CX3015]  
MB89P627P@SDIP64 [CX0064] MB89P627P@TQFP64 [CX3064]  
MB89P635@LQFP64 [CX3011] MB89P635@QFP64 [CX3015]  
MB89P635@SDIP64 [CX0064] MB89P635@TQFP64 [CX3064]  
MB89P635P@LQFP64 [CX3011] MB89P635P@QFP64 [CX3015]  
MB89P635P@SDIP64 [CX0064] MB89P635P@TQFP64 [CX3064]  
MB89P637@LQFP64 [CX3011] MB89P637@QFP64 [CX3015]  
MB89P637@SDIP64 [CX0064] MB89P637@TQFP64 [CX3064]  
MB89P637P@LQFP64 [CX3011] MB89P637P@QFP64 [CX3015]  
MB89P637P@SDIP64 [CX0064] MB89P637P@TQFP64 [CX3064]  
MB89P935ACP [CX0001] MB89P935CP--G-SH@SDIP32 [CX0032]  
MB89P935ACP--G-SH@SDIP32 [CX0032] MB89P935CP [CX0001] MB89P935CP--G-SH@SDIP32 [CX0032]  
MB90F036APMC@QFP120 [CX3028] MB90F057@LQFP100 [CX3021]  
MB90F057@QFP100 [CX3022] MB90F387PMT@LQFP48 [CX3047]  
MB90F387SPMT@LQFP48 [CX3047] MB90F455PMT@LQFP48 [CX3007]  
MB90F455SPMT@LQFP48 [CX3007] MB90F456PMT@LQFP48 [CX3007]  
MB90F456SPMT@LQFP48 [CX3007] MB90F457PMT@LQFP48 [CX3007]  
MB90F462APF@QFP64 [CX3049] MB90F462AP@SDIP64 [CX0064]  
MB90F462P@SDIP64 [CX0064] MB90F462APFM@LQFP64 [CX3012]  
MB90F462PFM@LQFP64 [CX3012] MB90F462PF@QFP64 [CX3049]  
MB90F553APFV@LQFP100 [CX3043] MB90F553APF@QFP100 [CX3023]  
MB90F553PFV@LQFP100 [CX3043] MB90F553PF@QFP100 [CX3023]  
MB90F562@QFP64 [CX3015] MB90F562@LQFP64 [CX3012]  
MB90F562B@LQFP64 [CX3012] MB90F562@SDIP64 [CX0064]  
MB90F562B@SDIP64 [CX0064] MB90F562B@QFP64 [CX3015]  
MB90F822APFM@LQFP80 [CX3017] MB90F822APF@PQFP80 [CX3019]  
MB90F822PF@PQFP80 [CX3019] MB90F822APFV@LQFP80 [CX3016]  
MB90F822PFV@LQFP80 [CX3016] MB90F822PFM@LQFP80 [CX3017]  
MB90F823APFM@LQFP80 [CX3017] MB90F823APF@PQFP80 [CX3019]  
MB90F823PF@PQFP80 [CX3019] MB90F823APFV@LQFP80 [CX3016]  
MB90F823PFV@LQFP80 [CX3016] MB90F823PFM@LQFP80 [CX3017]  
MB90F882@QFP100 [CX3022] MB90F882@LQFP100 [CX3021]  
MB90F884@QFP100 [CX3022] MB90F884@LQFP100 [CX3021]  
MB91F267NPMC-GE1@LQFP64 [CX3012] MB91F267NPMC-G@LQFP64 [CX3012]  
MB91F267NPMC-GSE1@LQFP64 [CX3012] MB91F267NPMC-GS@LQFP64 [CX3012]  
MB91F267PMC-G@LQFP64 [CX3012] MB91F267PMC-GE1@LQFP64 [CX3012]  
MB91F267PMC-GS@LQFP64 [CX3012] MB91F267PMC-GSE1@LQFP64 [CX3012]  
MB95F012KP [CX0032] MB95F012KPF [CX1033]  
MB95F012KPFT [CX1000] MB95F012KWQN [CX4015]  
MB95F013KP [CX0032] MB95F013KPF [CX3001]  
MB95F013KWQN [CX4015] MB95F014EPMC1 [CX3011]  
MB95F014EPMC2 [CX3012] MB95F114JAS@LQFP52 [CX3010]  
MB95F114JAW@LQFP52 [CX3010] MB95F114JS@LQFP52 [CX3010]  
MB95F114JW@LQFP52 [CX3010] MB95F114MAS@LQFP52 [CX3010]

MB95F114MAW@LQFP52 [CX3010]  
MB95F114MW@LQFP52 [CX3010]  
MB95F114NAW@LQFP52 [CX3010]  
MB95F114NW@LQFP52 [CX3010]  
MB95F116JAW@LQFP52 [CX3010]  
MB95F116JW@LQFP52 [CX3010]  
MB95F116MAW@LQFP52 [CX3010]  
MB95F116MW@LQFP52 [CX3010]  
MB95F116NAS@LQFP52(60K) [CX3010]  
MB95F116NS@LQFP52 [CX3010]  
MB95F118AS@LQFP48 [CX3047]  
MB95F118AW@LQFP48 [CX3047]  
MB95F118BS@LQFP48 [CX3047]  
MB95F118BW@LQFP48 [CX3047]  
MB95F118HS@LQFP48 [CX3047]  
MB95F118HW@LQFP48 [CX3047]  
MB95F118MS@LQFP48 [CX3047]  
MB95F118MW@LQFP48 [CX3047]  
MB95F118NS@LQFP48 [CX3047]  
MB95F118NW@LQFP48 [CX3047]  
MB95F118TS@LQFP48 [CX3047]  
MB95F118TW@LQFP48 [CX3047]  
MB95F128D@LQFP100 [CX3043]  
MB95F128E@LQFP100 [CX3043]  
MB95F128H@LQFP100 [CX3043]  
MB95F128J@LQFP100 [CX3043]  
MB95F128M@LQFP100 [CX3043]  
MB95F128N@LQFP100 [CX3043]  
MB95F128T@LQFP100 [CX3043]  
MB95F168JA@LQFP64 [CX3012]  
MB95F168JPMC@LQFP64 [CX3011]  
MB95F168MPMC@LQFP64 [CX3011]  
MB95F168NPMC@LQFP64 [CX3011]  
MB95F176JSPMC@LQFP64 [CX3012]  
MB95F176JWPMC@LQFP64 [CX3012]  
MB95F188@QFP80 [CX3016]  
MB95F202HAP@SDIP24 [CX0032]  
MB95F202HP@SDIP24 [CX0032]  
MB95F202KAP@SDIP24 [CX0032]  
MB95F202KP@SDIP24 [CX0032]  
MB95F203HAP@SDIP24 [CX0032]  
MB95F203HP@SDIP24 [CX0032]  
MB95F203KAP@SDIP24 [CX0032]  
MB95F203KP@SDIP24 [CX0032]  
MB95F204HAP@SDIP24 [CX0032]  
MB95F204HP@SDIP24 [CX0032]  
MB95F204KAP@SDIP24 [CX0032]  
MB95F204KP@SDIP24 [CX0032]  
MB95F212HPF@SOP8 [CX1044]  
MB95F212KPF@SOP8 [CX1044]  
MB95F213HPF@SOP8 [CX1044]  
MB95F213KPF@SOP8 [CX1044]  
MB95F214HPF@SOP8 [CX1044]  
MB95F214KPF@SOP8 [CX1044]  
MB95F222HPF@SOP16 [CX1032]  
MB95F222KPF@SOP16 [CX1032]  
MB95F223HPF@SOP16 [CX1032]  
MB95F223KPF@SOP16 [CX1032]  
MB95F224HPF@SOP16 [CX1032]

MB95F114MS@LQFP52 [CX3010]  
MB95F114NAS@LQFP52 [CX3010]  
MB95F114NS@LQFP52 [CX3010]  
MB95F116JAS@LQFP52 [CX3010]  
MB95F116JS@LQFP52 [CX3010]  
MB95F116MAS@LQFP52 [CX3010]  
MB95F116MS@LQFP52 [CX3010]  
MB95F116NAS@LQFP52 [CX3010]  
MB95F116NAW@LQFP52 [CX3010]  
MB95F116NW@LQFP52 [CX3010]  
MB95F118AS@LQFP52 [CX3010]  
MB95F118AW@LQFP52 [CX3010]  
MB95F118BS@LQFP52 [CX3010]  
MB95F118BW@LQFP52 [CX3010]  
MB95F118HS@LQFP52 [CX3010]  
MB95F118HW@LQFP52 [CX3010]  
MB95F118MS@LQFP52 [CX3010]  
MB95F118MW@LQFP52 [CX3010]  
MB95F118NS@LQFP52 [CX3010]  
MB95F118NW@LQFP52 [CX3010]  
MB95F118TS@LQFP52 [CX3010]  
MB95F118TW@LQFP52 [CX3010]  
MB95F128D@QFP100 [CX3022]  
MB95F128E@QFP100 [CX3022]  
MB95F128H@QFP100 [CX3022]  
MB95F128J@QFP100 [CX3022]  
MB95F128M@QFP100 [CX3022]  
MB95F128N@QFP100 [CX3022]  
MB95F128T@QFP100 [CX3022]  
MB95F168JA1@LQFP64 [CX3012]  
MB95F168JPMC1@LQFP64 [CX3011]  
MB95F168MPMC1@LQFP64 [CX3011]  
MB95F168NPMC1@LQFP64 [CX3011]  
MB95F176JSPMC1@LQFP64 [CX3011]  
MB95F176JWPMC1@LQFP64 [CX3011]  
MB95F188J@QFP80 [CX3016]  
MB95F202HAPF@SOP20 [CX1033]  
MB95F202HPF@SOP20 [CX1033]  
MB95F202KAPF@SOP20 [CX1033]  
MB95F202KPF@SOP20 [CX1033]  
MB95F203HAPF@SOP20 [CX1033]  
MB95F203HPF@SOP20 [CX1033]  
MB95F203KAPF@SOP20 [CX1033]  
MB95F203KPF@SOP20 [CX1033]  
MB95F204HAPF@SOP20 [CX1033]  
MB95F204HPF@SOP20 [CX1033]  
MB95F204KAPF@SOP20 [CX1033]  
MB95F204KPF@SOP20 [CX1033]  
MB95F212HPH [CX0001]  
MB95F212KPH [CX0001]  
MB95F213HPH [CX0001]  
MB95F213KPH [CX0001]  
MB95F214HPH [CX0001]  
MB95F214KPH [CX0001]  
MB95F222HPH [CX0001]  
MB95F222KPH [CX0001]  
MB95F223HPH [CX0001]  
MB95F223KPH [CX0001]  
MB95F224HPH [CX0001]

MB95F224KPF@SOP16 [CX1032] MB95F224KPH [CX0001]  
MB95F232HP@SDIP24 [CX0032] MB95F232HPF@SOP20 [CX1033]  
MB95F232KP@SDIP24 [CX0032] MB95F232KPF@SOP20 [CX1033]  
MB95F233HP@SDIP24 [CX0032] MB95F233HPF@SOP20 [CX1033]  
MB95F233KP@SDIP24 [CX0032] MB95F233KPF@SOP20 [CX1033]  
MB95F234HP@SDIP24 [CX0032] MB95F234HPF@SOP20 [CX1033]  
MB95F234KP@SDIP24 [CX0032] MB95F234KPF@SOP20 [CX1033]  
MB95F242HP [CX0001] MB95F242HPF@SOP8 [CX1032]  
MB95F242KP [CX0001] MB95F242KPF@SOP8 [CX1032]  
MB95F243HP [CX0001] MB95F243HPF@SOP8 [CX1032]  
MB95F243KP [CX0001] MB95F243KPF@SOP8 [CX1032]  
MB95F244HP [CX0001] MB95F244HPF@SOP8 [CX1032]  
MB95F244KP [CX0001] MB95F244KPF@SOP8 [CX1032]  
MB95F252HP [CX0001] MB95F252HPF@SOP16 [CX1032]  
MB95F252KP [CX0001] MB95F252KPF@SOP16 [CX1032]  
MB95F253HP [CX0001] MB95F253HPF@SOP16 [CX1032]  
MB95F253KP [CX0001] MB95F253KPF@SOP16 [CX1032]  
MB95F254HP [CX0001] MB95F254HPF@SOP16 [CX1032]  
MB95F254KP [CX0001] MB95F254KPF@SOP16 [CX1032]  
MB95F262HP@SDIP24 [CX0032] MB95F262HPF@SOP20 [CX1033]  
MB95F262HPFT [CX1000] MB95F262HPS@TSOP20 [CX1000]  
MB95F262HWQN [CX4015] MB95F262KP@SDIP24 [CX0032]  
MB95F262KPF@SOP20 [CX1033] MB95F262KPFT [CX1000]  
MB95F262KPS@TSOP20 [CX1000] MB95F262KWQN [CX4015]  
MB95F263HP@SDIP24 [CX0032] MB95F263HPF@SOP20 [CX1033]  
MB95F263HPFT [CX1000] MB95F263HPS@TSOP20 [CX1000]  
MB95F263HWQN [CX4015] MB95F263KP@SDIP24 [CX0032]  
MB95F263KPF@SOP20 [CX1033] MB95F263KPFT [CX1000]  
MB95F263KPS@TSOP20 [CX1000] MB95F263KWQN [CX4015]  
MB95F264HP@SDIP24 [CX0032] MB95F264HPF@SOP20 [CX1033]  
MB95F264HPFT [CX1000] MB95F264HPS@SSOP20 [CX1000]  
MB95F264HWQN [CX4015] MB95F264KP@SDIP24 [CX0032]  
MB95F264KPF@SOP20 [CX1033] MB95F264KPFT [CX1000]  
MB95F264KPS@SSOP20 [CX1000] MB95F264KWQN [CX4015]  
MB95F272HP [CX0001] MB95F272HPF@SOP8 [CX1032]  
MB95F272KP [CX0001] MB95F272KPF@SOP8 [CX1032]  
MB95F273HP [CX0001] MB95F273HPF@SOP8 [CX1032]  
MB95F273KP [CX0001] MB95F273KPF@SOP8 [CX1032]  
MB95F274HP [CX0001] MB95F274HPF@SOP8 [CX1032]  
MB95F274KP [CX0001] MB95F274KPF@SOP8 [CX1032]  
MB95F282HP [CX0001] MB95F282HPF@SOP16 [CX1032]  
MB95F282HWQN [CX4015] MB95F282KP [CX0001]  
MB95F282KPF@SOP16 [CX1032] MB95F282KWQN [CX4015]  
MB95F283HP [CX0001] MB95F283HPF@SOP16 [CX1032]  
MB95F283HWQN [CX4015] MB95F283KP [CX0001]  
MB95F283KPF@SOP16 [CX1032] MB95F283KWQN [CX4015]  
MB95F284HP [CX0001] MB95F284HPF@SOP16 [CX1032]  
MB95F284HWQN [CX4015] MB95F284KP [CX0001]  
MB95F284KPF@SOP16 [CX1032] MB95F284KWQN [CX4015]  
MB95F314E@QFP80 [CX3016]  
MB95F314E@QFP80(Parallel) [CX3016]  
MB95F314L@QFP80 [CX3016]  
MB95F314L@QFP80(Parallel) [CX3016]  
MB95F316E@QFP80 [CX3016]  
MB95F316E@QFP80(Parallel) [CX3016]  
MB95F316L@QFP80 [CX3016]  
MB95F316L@QFP80(Parallel) [CX3016]  
MB95F318E@QFP80 [CX3016]  
MB95F318E@QFP80(Parallel) [CX3016]

MB95F318L@QFP80 [CX3016]  
MB95F318L@QFP80(Parallel) [CX3016]  
MB95F332HP@SDIP32 [CX0032]  
MB95F332HP@SDIP32(Parallel) [CX0032]  
MB95F332HPF@LQFP32 [CX3001]  
MB95F332HPF@LQFP32(Parallel) [CX3001]  
MB95F332HWQN [CX4015]  
MB95F332HWQN@QFN32(Parallel) [CX4015]  
MB95F332KP@SDIP32 [CX0032]  
MB95F332KP@SDIP32(Parallel) [CX0032]  
MB95F332KPF@LQFP32 [CX3001]  
MB95F332KPF@LQFP32(Parallel) [CX3001]  
MB95F332KWQN [CX4015]  
MB95F332KWQN@QFN32(Parallel) [CX4015]  
MB95F333HP@SDIP32 [CX0032]  
MB95F333HP@SDIP32(Parallel) [CX0032]  
MB95F333HPF@LQFP32 [CX3001]  
MB95F333HPF@LQFP32(Parallel) [CX3001]  
MB95F333HWQN [CX4015]  
MB95F333HWQN@QFN32(Parallel) [CX4015]  
MB95F333KP@SDIP32 [CX0032]  
MB95F333KP@SDIP32(Parallel) [CX0032]  
MB95F333KPF@LQFP32 [CX3001]  
MB95F333KPF@LQFP32(Parallel) [CX3001]  
MB95F333KWQN [CX4015]  
MB95F333KWQN@QFN32(Parallel) [CX4015]  
MB95F334HP@SDIP32 [CX0032]  
MB95F334HP@SDIP32(Parallel) [CX0032]  
MB95F334HPF@LQFP32 [CX3001]  
MB95F334HPF@LQFP32(Parallel) [CX3001]  
MB95F334HWQN [CX4015]  
MB95F334HWQN@QFN32(Parallel) [CX4015]  
MB95F334KP@SDIP32 [CX0032]  
MB95F334KP@SDIP32(Parallel) [CX0032]  
MB95F334KPF@LQFP32 [CX3001]  
MB95F334KPF@LQFP32(Parallel) [CX3001]  
MB95F334KWQN [CX4015]  
MB95F334KWQN@QFN32(Parallel) [CX4015]  
MB95F352E@QFP32(Parallel) [CX3001]  
MB95F352E@SOIC24(Parallel) [CX1033]  
MB95F352E@SSOP24(Parallel) [CX1001]  
MB95F352L@QFP32(Parallel) [CX3001]  
MB95F352L@SOIC24(Parallel) [CX1033]  
MB95F352L@SSOP24(Parallel) [CX1001]  
MB95F353E@QFP32(Parallel) [CX3001]  
MB95F353E@SOIC24(Parallel) [CX1033]  
MB95F353E@SSOP24(Parallel) [CX1001]  
MB95F353L@QFP32(Parallel) [CX3001]  
MB95F353L@SOIC24(Parallel) [CX1033]  
MB95F353L@SSOP24(Parallel) [CX1001]  
MB95F354E@QFP32(Parallel) [CX3001]  
MB95F354E@SOIC24(Parallel) [CX1033]  
MB95F354E@SSOP24(Parallel) [CX1001]  
MB95F354L@QFP32(Parallel) [CX3001]  
MB95F354L@SOIC24(Parallel) [CX1033]  
MB95F354L@SSOP24(Parallel) [CX1001]  
MB95F374E@LQFP64 [CX3057]  
MB95F374E@LQFP64(Parallel) [CX3057]  
MB95F374E@QFP64 [CX3064]

MB95F374E@QFP64(Parallel) [CX3064]  
MB95F374L@LQFP64 [CX3057]  
MB95F374L@LQFP64(Parallel) [CX3057]  
MB95F374L@QFP64 [CX3064]  
MB95F374L@QFP64(Parallel) [CX3064]  
MB95F376E@LQFP64 [CX3057]  
MB95F376E@LQFP64(Parallel) [CX3057]  
MB95F376E@QFP64 [CX3064]  
MB95F376E@QFP64(Parallel) [CX3064]  
MB95F376L@LQFP64 [CX3057]  
MB95F376L@LQFP64(Parallel) [CX3057]  
MB95F376L@QFP64 [CX3064]  
MB95F376L@QFP64(Parallel) [CX3064]  
MB95F378E@LQFP64 [CX3057]  
MB95F378E@LQFP64(Parallel) [CX3057]  
MB95F378E@QFP64 [CX3064]  
MB95F378E@QFP64(Parallel) [CX3064]  
MB95F378L@LQFP64 [CX3057]  
MB95F378L@LQFP64(Parallel) [CX3057]  
MB95F378L@QFP64 [CX3064]  
MB95F378L@QFP64(Parallel) [CX3064]  
MB95F394H@QFN48 [CX4021]  
MB95F394H@QFN48(Parallel) [CX4021]  
MB95F394H@QFP48 [CX3007]  
MB95F394H@QFP48(Parallel) [CX3007]  
MB95F394H@QFP52 [CX3010]  
MB95F394H@QFP52(Parallel) [CX3010]  
MB95F394K@QFN48 [CX4021]  
MB95F394K@QFN48(Parallel) [CX4021]  
MB95F394K@QFP48 [CX3007]  
MB95F394K@QFP48(Parallel) [CX3007]  
MB95F394K@QFP52 [CX3010]  
MB95F394K@QFP52(Parallel) [CX3010]  
MB95F396H@QFN48 [CX4021]  
MB95F396H@QFN48(Parallel) [CX4021]  
MB95F396H@QFP48 [CX3007]  
MB95F396H@QFP48(Parallel) [CX3007]  
MB95F396H@QFP52 [CX3010]  
MB95F396H@QFP52(Parallel) [CX3010]  
MB95F396K@QFN48 [CX4021]  
MB95F396K@QFN48(Parallel) [CX4021]  
MB95F396K@QFP48 [CX3007]  
MB95F396K@QFP48(Parallel) [CX3007]  
MB95F396K@QFP52 [CX3010]  
MB95F396K@QFP52(Parallel) [CX3010]  
MB95F398H@QFN48 [CX4021]  
MB95F398H@QFN48(Parallel) [CX4021]  
MB95F398H@QFP48 [CX3007]  
MB95F398H@QFP48(Parallel) [CX3007]  
MB95F398H@QFP52 [CX3010]  
MB95F398H@QFP52(Parallel) [CX3010]  
MB95F398K@QFN48 [CX4021]  
MB95F398K@QFN48(Parallel) [CX4021]  
MB95F398K@QFP48 [CX3007]  
MB95F398K@QFP48(Parallel) [CX3007]  
MB95F398K@QFP52 [CX3010]  
MB95F398K@QFP52(Parallel) [CX3010]  
MB95F414HPMC [CX3016]  
MB95F416HPMC [CX3016]

MB95F414KPMC [CX3016]  
MB95F416KPMC [CX3016]

MB95F418HPMC [CX3016]	MB95F418KPMC [CX3016]
MB95F432HP@SDIP32(Parallel) [CX0032]	
MB95F432HPF@LQFP32(Parallel) [CX3001]	
MB95F432KP@SDIP32(Parallel) [CX0032]	
MB95F432KPF@LQFP32(Parallel) [CX3001]	
MB95F433HP@SDIP32(Parallel) [CX0032]	
MB95F433HPF@LQFP32(Parallel) [CX3001]	
MB95F433KP@SDIP32(Parallel) [CX0032]	
MB95F433KPF@LQFP32(Parallel) [CX3001]	
MB95F434HP@SDIP32(Parallel) [CX0032]	
MB95F434HPF@LQFP32(Parallel) [CX3001]	
MB95F434KP@SDIP32(Parallel) [CX0032]	
MB95F434KPF@LQFP32(Parallel) [CX3001]	
MB95F474HPMC1 [CX3011]	MB95F474HPMC2 [CX3012]
MB95F474KPMC1 [CX3011]	MB95F474KPMC2 [CX3012]
MB95F476HPMC1 [CX3011]	MB95F476HPMC2 [CX3012]
MB95F476KPMC1 [CX3011]	MB95F476KPMC2 [CX3012]
MB95F478HPMC1 [CX3011]	MB95F478HPMC2 [CX3012]
MB95F478KPMC1 [CX3011]	MB95F478KPMC2 [CX3012]
MB95F562HP [CX0032]	MB95F562HPF [CX1033]
MB95F562HPFT [CX1000]	MB95F562HPS [CX1000]
MB95F562HWQN [CX4015]	MB95F562KP [CX0032]
MB95F562KPF [CX1033]	MB95F562KPFT [CX1000]
MB95F562KPS [CX1000]	MB95F562KWQN [CX4015]
MB95F563HP [CX0032]	MB95F563HPF [CX1033]
MB95F563HPFT [CX1000]	MB95F563HPS [CX1000]
MB95F563HWQN [CX4015]	MB95F563KP [CX0032]
MB95F563KPF [CX1033]	MB95F563KPFT [CX1000]
MB95F563KPS [CX1000]	MB95F563KWQN [CX4015]
MB95F564HP [CX0032]	MB95F564HPF [CX1033]
MB95F564HPFT [CX1000]	MB95F564HPS [CX1000]
MB95F564HWQN [CX4015]	MB95F564KP [CX0032]
MB95F564KPF [CX1033]	MB95F564KPFT [CX1000]
MB95F564KPS [CX1000]	MB95F564KWQN [CX4015]
MB95F572HP [CX0001]	MB95F572HPF [CX1032]
MB95F572KP [CX0001]	MB95F572KPF [CX1032]
MB95F573HP [CX0001]	MB95F573HPF [CX1032]
MB95F573KP [CX0001]	MB95F573KPF [CX1032]
MB95F574HP [CX0001]	MB95F574HPF [CX1032]
MB95F574KP [CX0001]	MB95F574KPF [CX1032]
MB95F582HP [CX0001]	MB95F582HPF [CX1032]
MB95F582HWQN [CX4015]	MB95F582KP [CX0001]
MB95F582KPF [CX1032]	MB95F582KWQN [CX4015]
MB95F583HP [CX0001]	MB95F583HPF [CX1032]
MB95F583HWQN [CX4015]	MB95F583KP [CX0001]
MB95F583KPF [CX1032]	MB95F583KWQN [CX4015]
MB95F584HP [CX0001]	MB95F584HPF [CX1032]
MB95F584HWQN [CX4015]	MB95F584KP [CX0001]
MB95F584KPF [CX1032]	MB95F584KWQN [CX4015]
MB95F632HP [CX0032]	MB95F632HPF [CX3001]
MB95F632HWQN [CX4015]	MB95F632KP [CX0032]
MB95F632KPF [CX3001]	MB95F632KWQN [CX4015]
MB95F633HP [CX0032]	MB95F633HPF [CX3001]
MB95F633HWQN [CX4015]	MB95F633KP [CX0032]
MB95F633KPF [CX3001]	MB95F633KWQN [CX4015]
MB95F634HP [CX0032]	MB95F634HPF [CX3001]
MB95F634HWQN [CX4015]	MB95F634KP [CX0032]
MB95F634KPF [CX3001]	MB95F634KWQN [CX4015]
MB95F636HP [CX0032]	MB95F636HPF [CX3001]

MB95F636HWQN [CX4015]  
MB95F636KPF [CX3001]  
MB95F652E@QFN32 [CX4015]  
MB95F652E@SOIC24 [CX1033]  
MB95F652L@QFN32 [CX4015]  
MB95F652L@SOIC24 [CX1033]  
MB95F653E@QFN32 [CX4015]  
MB95F653E@SOIC24 [CX1033]  
MB95F653L@QFN32 [CX4015]  
MB95F653L@SOIC24 [CX1033]  
MB95F654E@QFN32 [CX4015]  
MB95F654E@SOIC24 [CX1033]  
MB95F654L@QFN32 [CX4015]  
MB95F654L@SOIC24 [CX1033]  
MB95F656E@QFN32 [CX4015]  
MB95F656E@SOIC24 [CX1033]  
MB95F656L@QFN32 [CX4015]  
MB95F656L@SOIC24 [CX1033]  
MB95F694K@QFN48 [CX4021]  
MB95F694K@QFP52 [CX3010]  
MB95F696K@QFP48 [CX3007]  
MB95F698K@QFN48 [CX4021]  
MB95F698K@QFP52 [CX3010]  
MB95F714LPMC [CX3016]  
MB95F716LPMC [CX3016]  
MB95F718LPMC [CX3016]  
MB95F774EPMC2 [CX3012]  
MB95F774LPMC2 [CX3012]  
MB95F776EPMC2 [CX3012]  
MB95F776LPMC2 [CX3012]  
MB95F778EPMC2 [CX3012]  
MB95F778LPMC2 [CX3012]  
MB95F814EPMC1 [CX3057-12]  
MB95F814KPMC1 [CX3057-12]  
MB95F814LPMC1 [CX3057-12]  
MB95F816EPMC1 [CX3057-12]  
MB95F816KPMC1 [CX3057-12]  
MB95F816LPMC1 [CX3057-12]  
MB95F818EPMC1 [CX3057-12]  
MB95F818KPMC1 [CX3057-12]  
MB95F818LPMC1 [CX3057-12]  
MB95F876K@QFP52 [CX3010]  
MB95R202HAPF@SOP20 [CX1033]  
MB95R202HPF@SOP20 [CX1033]  
MB95R202KAPF@SOP20 [CX1033]  
MB95R202KPF@SOP20 [CX1033]  
MB95R203HAPF@SOP20 [CX1033]  
MB95R203HPF@SOP20 [CX1033]  
MB95R203KAPF@SOP20 [CX1033]  
MB95R203KPF@SOP20 [CX1033]  
MB95R204HAPF@SOP20 [CX1033]  
MB95R204HPF@SOP20 [CX1033]  
MB95R204KAPF@SOP20 [CX1033]  
MB95R204KPF@SOP20 [CX1033]  
MB95R212HPH [CX0001]  
MB95R212KPH [CX0001]  
MB95R213HPH [CX0001]  
MB95R213KPH [CX0001]  
MB95R214HPH [CX0001]

MB95F636KP [CX0032]  
MB95F636KWQN [CX4015]  
MB95F652E@QFP32 [CX3001]  
MB95F652E@SSOP24 [CX1001]  
MB95F652L@QFP32 [CX3001]  
MB95F652L@SSOP24 [CX1001]  
MB95F653E@QFP32 [CX3001]  
MB95F653E@SSOP24 [CX1001]  
MB95F653L@QFP32 [CX3001]  
MB95F653L@SSOP24 [CX1001]  
MB95F654E@QFP32 [CX3001]  
MB95F654E@SSOP24 [CX1001]  
MB95F654L@QFP32 [CX3001]  
MB95F654L@SSOP24 [CX1001]  
MB95F656E@QFP32 [CX3001]  
MB95F656E@SSOP24 [CX1001]  
MB95F656L@QFP32 [CX3001]  
MB95F656L@SSOP24 [CX1001]  
MB95F694K@QFP48 [CX3007]  
MB95F696K@QFN48 [CX4021]  
MB95F696K@QFP52 [CX3010]  
MB95F698K@QFP48 [CX3007]  
MB95F714EPMC [CX3016]  
MB95F716EPMC [CX3016]  
MB95F718EPMC [CX3016]  
MB95F774EPMC1 [CX3011]  
MB95F774LPMC1 [CX3011]  
MB95F776EPMC1 [CX3011]  
MB95F776LPMC1 [CX3011]  
MB95F778EPMC1 [CX3011]  
MB95F778LPMC1 [CX3011]  
MB95F814EPMC [CX3012-1]  
MB95F814KPMC [CX3012-1]  
MB95F814LPMC [CX3012-1]  
MB95F816EPMC [CX3012-1]  
MB95F816KPMC [CX3012-1]  
MB95F816LPMC [CX3012-1]  
MB95F818EPMC [CX3012-1]  
MB95F818KPMC [CX3012-1]  
MB95F818LPMC [CX3012-1]  
MB95F876K@QFP48 [CX3007]  
MB95R202HAP@SDIP24 [CX0032]  
MB95R202HP@SDIP24 [CX0032]  
MB95R202KAP@SDIP24 [CX0032]  
MB95R202KP@SDIP24 [CX0032]  
MB95R203HAP@SDIP24 [CX0032]  
MB95R203HP@SDIP24 [CX0032]  
MB95R203KAP@SDIP24 [CX0032]  
MB95R203KP@SDIP24 [CX0032]  
MB95R204HAP@SDIP24 [CX0032]  
MB95R204HP@SDIP24 [CX0032]  
MB95R204KAP@SDIP24 [CX0032]  
MB95R204KP@SDIP24 [CX0032]  
MB95R212HPF@SOP8 [CX1044]  
MB95R212KPF@SOP8 [CX1044]  
MB95R213HPF@SOP8 [CX1044]  
MB95R213KPF@SOP8 [CX1044]  
MB95R214HPF@SOP8 [CX1044]  
MB95R214KPF@SOP8 [CX1044]







MB96F615ABPMC@LQFP48 [CX3007]  
MB96F615RBPMC@LQFP48 [CX3007]  
MB96F622AAPMC1 [CX3011]  
MB96F622ABPMC1 [CX3011]  
MB96F622RAPMC1 [CX3011]  
MB96F622RBPMC1 [CX3011]  
MB96F623AAPMC1 [CX3011]  
MB96F623ABPMC1 [CX3011]  
MB96F623RAPMC1 [CX3011]  
MB96F623RBPMC1 [CX3011]  
MB96F625AAPMC1 [CX3011]  
MB96F625ABPMC1 [CX3011]  
MB96F625RAPMC1 [CX3011]  
MB96F625RBPMC1 [CX3011]  
MB96F673AAPMC1 [CX3011]  
MB96F673ABPMC1 [CX3011]  
MB96F673RAPMC1 [CX3011]  
MB96F673RBPMC1 [CX3011]  
MB96F675AAPMC1 [CX3011]  
MB96F675ABPMC1 [CX3011]  
MB96F675RAPMC1 [CX3011]  
MB96F675RBPMC1 [CX3011]  
MB96F683ABPMC [CX3016]  
MB96F683RBPMC [CX3016]  
MB96F685ABPMC [CX3016]  
MB96F685RBPMC [CX3016]  
MB96F693ABPMC [CX3043]  
MB96F693RBPMC [CX3043]  
MB96F695ABPMC [CX3043]  
MB96F695RBPMC [CX3043]  
MB96F696ABPMC [CX3043]  
MB96F696RBPMC [CX3043]  
MB96F6A3ABPMC [CX3027]  
MB96F6A3RBPMC [CX3027]  
MB96F6A5ABPMC [CX3027]  
MB96F6A5RBPMC [CX3027]  
MB96F6A6ABPMC [CX3027]  
MB96F6A6RBPMC [CX3027]  
MB96F6B3ABPMC [CX3043]  
MB96F6B3RBPMC [CX3043]  
MB96F6B5ABPMC [CX3043]  
MB96F6B5RBPMC [CX3043]  
MB96F6B6ABPMC [CX3043]  
MB96F6B6RBPMC [CX3043]  
MB96F6C3ABPMC [CX3027]  
MB96F6C3RBPMC [CX3027]  
MB96F6C5ABPMC [CX3027]  
MB96F6C5RBPMC [CX3027]  
MB96F6C6ABPMC [CX3027]  
MB96F6C6RBPMC [CX3027]  
MB9AF007KAQN [CX4021]  
MB9AF007KQN [CX4021]  
MB9AF007LAPMC1 [CX3011]  
MB9AF007LPMC [CX3064]  
MB9AF007LQN [CX4023]  
MB9AF007MAPMC1 [CX3017]  
MB9AF007MPMC1 [CX3017]  
MB9AF007NAPF [CX3077]  
MB9AF007NBGL [BBBB]

MB96F615RAPMC@LQFP48 [CX3007]  
MB96F622AAPMC [CX3064]  
MB96F622ABPMC [CX3064]  
MB96F622RAPMC [CX3064]  
MB96F622RBPMC [CX3064]  
MB96F623AAPMC [CX3064]  
MB96F623ABPMC [CX3064]  
MB96F623RAPMC [CX3064]  
MB96F623RBPMC [CX3064]  
MB96F625AAPMC [CX3064]  
MB96F625ABPMC [CX3064]  
MB96F625RAPMC [CX3064]  
MB96F625RBPMC [CX3064]  
MB96F673AAPMC [CX3064]  
MB96F673ABPMC [CX3064]  
MB96F673RAPMC [CX3064]  
MB96F673RBPMC [CX3064]  
MB96F675AAPMC [CX3064]  
MB96F675ABPMC [CX3064]  
MB96F675RAPMC [CX3064]  
MB96F675RBPMC [CX3064]  
MB96F683AAPMC [CX3016]  
MB96F683RAPMC [CX3016]  
MB96F685AAPMC [CX3016]  
MB96F685RAPMC [CX3016]  
MB96F693AAPMC [CX3043]  
MB96F693RAPMC [CX3043]  
MB96F695AAPMC [CX3043]  
MB96F695RAPMC [CX3043]  
MB96F696AAPMC [CX3043]  
MB96F696RAPMC [CX3043]  
MB96F6A3AAPMC [CX3027]  
MB96F6A3RAPMC [CX3027]  
MB96F6A5AAPMC [CX3027]  
MB96F6A5RAPMC [CX3027]  
MB96F6A6AAPMC [CX3027]  
MB96F6A6RAPMC [CX3027]  
MB96F6B3AAPMC [CX3043]  
MB96F6B3RAPMC [CX3043]  
MB96F6B5AAPMC [CX3043]  
MB96F6B5RAPMC [CX3043]  
MB96F6B6AAPMC [CX3043]  
MB96F6B6RAPMC [CX3043]  
MB96F6C3AAPMC [CX3027]  
MB96F6C3RAPMC [CX3027]  
MB96F6C5AAPMC [CX3027]  
MB96F6C5RAPMC [CX3027]  
MB96F6C6AAPMC [CX3027]  
MB96F6C6RAPMC [CX3027]  
MB9AF007KAPMC [CX3007]  
MB9AF007KPMC [CX3007]  
MB9AF007LAPMC [CX3064]  
MB9AF007LAQN [CX4023]  
MB9AF007LPMC1 [CX3011]  
MB9AF007MAPMC [CX3016]  
MB9AF007MPMC [CX3016]  
MB9AF007NABGL [BBBB]  
MB9AF007NAPMC [CX3021]  
MB9AF007NPF [CX3077]

MB9AF007NPMC [CX3021]  
MB9AF111KPMC1 [CX3063]  
MB9AF111LPMC [CX3064]  
MB9AF111MPMC [CX3016]  
MB9AF111NPF [CX3077]  
MB9AF112KPMC [CX3007]  
MB9AF112KQN [CX4021]  
MB9AF112LPMC1 [CX3011]  
MB9AF112NBGL [BBBB]  
MB9AF112NPMC [CX3021]  
MB9AF114KPMC1 [CX3063]  
MB9AF114LPMC [CX3064]  
MB9AF114MPMC [CX3016]  
MB9AF114NPF [CX3077]  
MB9AF115KPMC [CX3007]  
MB9AF115KQN [CX4021]  
MB9AF115LPMC1 [CX3011]  
MB9AF115NBGL [BBBB]  
MB9AF115NPMC [CX3021]  
MB9AF116KPMC1 [CX3063]  
MB9AF116LPMC [CX3064]  
MB9AF116MPMC [CX3016]  
MB9AF116NPF [CX3077]  
MB9AF131KAPMC [CX3007]  
MB9AF131KPMC [CX3007]  
MB9AF131LAPMC [CX3064]  
MB9AF131LAQN [CX4023]  
MB9AF131LPMC1 [CX3011]  
MB9AF131MAPMC [CX3016]  
MB9AF131MPMC [CX3016]  
MB9AF131NABGL [BBBB]  
MB9AF131NAPMC [CX3021]  
MB9AF131NPF [CX3077]  
MB9AF132KAPMC [CX3007]  
MB9AF132KPMC [CX3007]  
MB9AF132LAPMC [CX3064]  
MB9AF132LAQN [CX4023]  
MB9AF132LPMC1 [CX3011]  
MB9AF132MAPMC [CX3016]  
MB9AF132MPMC [CX3016]  
MB9AF132NABGL [BBBB]  
MB9AF132NAPMC [CX3021]  
MB9AF132NPF [CX3077]  
MB9AF134KAPMC [CX3007]  
MB9AF134KPMC [CX3007]  
MB9AF134LAPMC [CX3064]  
MB9AF134LAQN [CX4023]  
MB9AF134LPMC1 [CX3011]  
MB9AF134MAPMC [CX3016]  
MB9AF134MPMC [CX3016]  
MB9AF134NABGL [BBBB]  
MB9AF134NAPMC [CX3021]  
MB9AF134NPF [CX3077]  
MB9AF135KAPMC [CX3007]  
MB9AF135KPMC [CX3007]  
MB9AF135LAPMC [CX3064]  
MB9AF135LAQN [CX4023]  
MB9AF135LPMC1 [CX3011]  
MB9AF135MAPMC [CX3016]

MB9AF111KPMC [CX3007]  
MB9AF111KQN [CX4021]  
MB9AF111LPMC1 [CX3011]  
MB9AF111NBGL [BBBB]  
MB9AF111NPMC [CX3021]  
MB9AF112KPMC1 [CX3063]  
MB9AF112LPMC [CX3064]  
MB9AF112MPMC [CX3016]  
MB9AF112NPF [CX3077]  
MB9AF114KPMC [CX3007]  
MB9AF114KQN [CX4021]  
MB9AF114LPMC1 [CX3011]  
MB9AF114NBGL [BBBB]  
MB9AF114NPMC [CX3021]  
MB9AF115KPMC1 [CX3063]  
MB9AF115LPMC [CX3064]  
MB9AF115MPMC [CX3016]  
MB9AF115NPF [CX3077]  
MB9AF116KPMC [CX3007]  
MB9AF116KQN [CX4021]  
MB9AF116LPMC1 [CX3011]  
MB9AF116NBGL [BBBB]  
MB9AF116NPMC [CX3021]  
MB9AF131KAQN [CX4021]  
MB9AF131KQN [CX4021]  
MB9AF131LAPMC1 [CX3011]  
MB9AF131LPMC [CX3064]  
MB9AF131LQN [CX4023]  
MB9AF131MAPMC1 [CX3017]  
MB9AF131MPMC1 [CX3017]  
MB9AF131NAPF [CX3077]  
MB9AF131NBGL [BBBB]  
MB9AF131NPMC [CX3021]  
MB9AF132KAQN [CX4021]  
MB9AF132KQN [CX4021]  
MB9AF132LAPMC1 [CX3011]  
MB9AF132LPMC [CX3064]  
MB9AF132LQN [CX4023]  
MB9AF132MAPMC1 [CX3017]  
MB9AF132MPMC1 [CX3017]  
MB9AF132NAPF [CX3077]  
MB9AF132NBGL [BBBB]  
MB9AF132NPMC [CX3021]  
MB9AF134KAQN [CX4021]  
MB9AF134KQN [CX4021]  
MB9AF134LAPMC1 [CX3011]  
MB9AF134LPMC [CX3064]  
MB9AF134LQN [CX4023]  
MB9AF134MAPMC1 [CX3017]  
MB9AF134MPMC1 [CX3017]  
MB9AF134NAPF [CX3077]  
MB9AF134NBGL [BBBB]  
MB9AF134NPMC [CX3021]  
MB9AF135KAQN [CX4021]  
MB9AF135KQN [CX4021]  
MB9AF135LAPMC1 [CX3011]  
MB9AF135LPMC [CX3064]  
MB9AF135LQN [CX4023]  
MB9AF135MAPMC1 [CX3017]

MB9AF135MPMC [CX3016]  
MB9AF135NABGL [BBBB]  
MB9AF135NAPMC [CX3021]  
MB9AF135NPF [CX3077]  
MB9AF136KAPMC [CX3007]  
MB9AF136KPMC [CX3007]  
MB9AF136LAPMC [CX3064]  
MB9AF136LAQN [CX4023]  
MB9AF136LPMC1 [CX3011]  
MB9AF136MAPMC [CX3016]  
MB9AF136MPMC [CX3016]  
MB9AF136NABGL [BBBB]  
MB9AF136NAPMC [CX3021]  
MB9AF136NPF [CX3077]  
MB9AF311KPMC [CX3007]  
MB9AF311KQN [CX4021]  
MB9AF311LPMC1 [CX3011]  
MB9AF311NBGL [BBBB]  
MB9AF311NPMC [CX3021]  
MB9AF312KPMC1 [CX3063]  
MB9AF312LPMC [CX3064]  
MB9AF312MPMC [CX3016]  
MB9AF312NPF [CX3077]  
MB9AF314KPMC [CX3007]  
MB9AF314KQN [CX4021]  
MB9AF314LPMC1 [CX3011]  
MB9AF314NBGL [BBBB]  
MB9AF314NPMC [CX3021]  
MB9AF315KPMC1 [CX3063]  
MB9AF315LPMC [CX3064]  
MB9AF315MPMC [CX3016]  
MB9AF315NPF [CX3077]  
MB9AF316KPMC [CX3007]  
MB9AF316KQN [CX4021]  
MB9AF316LPMC1 [CX3011]  
MB9AF316NBGL [BBBB]  
MB9AF316NPMC [CX3021]  
MB9AFA31KAQN [CX4021]  
MB9AFA31KQN [CX4021]  
MB9AFA31LAPMC1 [CX3011]  
MB9AFA31LPMC [CX3064]  
MB9AFA31LQN [CX4023]  
MB9AFA31MAPMC1 [CX3017]  
MB9AFA31MPMC1 [CX3017]  
MB9AFA31NAPF [CX3077]  
MB9AFA31NBGL [BBBB]  
MB9AFA31NPMC [CX3021]  
MB9AFA32KAQN [CX4021]  
MB9AFA32KQN [CX4021]  
MB9AFA32LAPMC1 [CX3011]  
MB9AFA32LPMC [CX3064]  
MB9AFA32LQN [CX4023]  
MB9AFA32MAPMC1 [CX3017]  
MB9AFA32MPMC1 [CX3017]  
MB9AFA32NAPF [CX3077]  
MB9AFA32NBGL [BBBB]  
MB9AFA32NPMC [CX3021]  
MB9AFA34KAQN [CX4021]  
MB9AFA34KQN [CX4021]

MB9AF135MPMC1 [CX3017]  
MB9AF135NAPF [CX3077]  
MB9AF135NBGL [BBBB]  
MB9AF135NPMC [CX3021]  
MB9AF136KAQN [CX4021]  
MB9AF136KQN [CX4021]  
MB9AF136LAPMC1 [CX3011]  
MB9AF136LPMC [CX3064]  
MB9AF136LQN [CX4023]  
MB9AF136MAPMC1 [CX3017]  
MB9AF136MPMC1 [CX3017]  
MB9AF136NAPF [CX3077]  
MB9AF136NBGL [BBBB]  
MB9AF136NPMC [CX3021]  
MB9AF311KPMC1 [CX3063]  
MB9AF311LPMC [CX3064]  
MB9AF311MPMC [CX3016]  
MB9AF311NPF [CX3077]  
MB9AF312KPMC [CX3007]  
MB9AF312KQN [CX4021]  
MB9AF312LPMC1 [CX3011]  
MB9AF312NBGL [BBBB]  
MB9AF312NPMC [CX3021]  
MB9AF314KPMC1 [CX3063]  
MB9AF314LPMC [CX3064]  
MB9AF314MPMC [CX3016]  
MB9AF314NPF [CX3077]  
MB9AF315KPMC [CX3007]  
MB9AF315KQN [CX4021]  
MB9AF315LPMC1 [CX3011]  
MB9AF315NBGL [BBBB]  
MB9AF315NPMC [CX3021]  
MB9AF316KPMC1 [CX3063]  
MB9AF316LPMC [CX3064]  
MB9AF316MPMC [CX3016]  
MB9AF316NPF [CX3077]  
MB9AFA31KAPMC [CX3007]  
MB9AFA31KPMC [CX3007]  
MB9AFA31LAPMC [CX3064]  
MB9AFA31LAQN [CX4023]  
MB9AFA31LPMC1 [CX3011]  
MB9AFA31MAPMC [CX3016]  
MB9AFA31MPMC [CX3016]  
MB9AFA31NABGL [BBBB]  
MB9AFA31NAPMC [CX3021]  
MB9AFA31NPF [CX3077]  
MB9AFA32KAPMC [CX3007]  
MB9AFA32KPMC [CX3007]  
MB9AFA32LAPMC [CX3064]  
MB9AFA32LAQN [CX4023]  
MB9AFA32LPMC1 [CX3011]  
MB9AFA32MAPMC [CX3016]  
MB9AFA32MPMC [CX3016]  
MB9AFA32NABGL [BBBB]  
MB9AFA32NAPMC [CX3021]  
MB9AFA32NPF [CX3077]  
MB9AFA34KAPMC [CX3007]  
MB9AFA34KPMC [CX3007]  
MB9AFA34LAPMC [CX3064]

MB9AFA34LAPMC1 [CX3011]  
MB9AFA34LPMC [CX3064]  
MB9AFA34LQN [CX4023]  
MB9AFA34MAPMC1 [CX3017]  
MB9AFA34MPMC1 [CX3017]  
MB9AFA34NAPF [CX3077]  
MB9AFA34NBGL [BBBB]  
MB9AFA34NPMC [CX3021]  
MB9AFA35KAQN [CX4021]  
MB9AFA35KQN [CX4021]  
MB9AFA35LAPMC1 [CX3011]  
MB9AFA35LPMC [CX3064]  
MB9AFA35LQN [CX4023]  
MB9AFA35MAPMC1 [CX3017]  
MB9AFA35MPMC1 [CX3017]  
MB9AFA35NAPF [CX3077]  
MB9AFA35NBGL [BBBB]  
MB9AFA35NPMC [CX3021]  
MB9AFA36KAQN [CX4021]  
MB9AFA36KQN [CX4021]  
MB9AFA36LAPMC1 [CX3011]  
MB9AFA36LPMC [CX3064]  
MB9AFA36LQN [CX4023]  
MB9AFA36MAPMC1 [CX3017]  
MB9AFA36MPMC1 [CX3017]  
MB9AFA36NAPF [CX3077]  
MB9AFA36NBGL [BBBB]  
MB9AFA36NPMC [CX3021]  
MBG043(old) [CX0001]  
MBG048(old) [CX0001]

MB9AFA34LAQN [CX4023]  
MB9AFA34LPMC1 [CX3011]  
MB9AFA34MAPMC [CX3016]  
MB9AFA34MPMC [CX3016]  
MB9AFA34NABGL [BBBB]  
MB9AFA34NAPMC [CX3021]  
MB9AFA34NPF [CX3077]  
MB9AFA35KAPMC [CX3007]  
MB9AFA35KPMC [CX3007]  
MB9AFA35LAPMC [CX3064]  
MB9AFA35LAQN [CX4023]  
MB9AFA35LPMC1 [CX3011]  
MB9AFA35MAPMC [CX3016]  
MB9AFA35MPMC [CX3016]  
MB9AFA35NABGL [BBBB]  
MB9AFA35NAPMC [CX3021]  
MB9AFA35NPF [CX3077]  
MB9AFA36KAPMC [CX3007]  
MB9AFA36KPMC [CX3007]  
MB9AFA36LAPMC [CX3064]  
MB9AFA36LAQN [CX4023]  
MB9AFA36LPMC1 [CX3011]  
MB9AFA36MAPMC [CX3016]  
MB9AFA36MPMC [CX3016]  
MB9AFA36NABGL [BBBB]  
MB9AFA36NAPMC [CX3021]  
MB9AFA36NPF [CX3077]  
MBG043 [CX5214]  
MBG048 [CX5214]

## FULLRICH

### MICROCONTROLLER

CY8C20434@QFN32 [CX4015]  
CY8C20437S@MLF32 [CX4015]  
CY8C20447S@MLF32 [CX4015]  
CY8C20467S@MLF32 [CX4015]  
CY8C20497S@MLF32 [CX4015]  
CY8C21434B@QFN32 [CX4015]  
CY8C21634B@QFN32 [CX4015]  
CY8CTMA140@QFN36 [CX4042]  
CY8CTMA140E [CX0001]  
CY8CTMA140E@QFN48 [CX4043]  
CY8CTMA300E@QFN48 [CX4043]  
CY8CTMA340@QFN48 [CX4043]  
CY8CTMA375@QFN48 [CX4043]  
CY8CTMA375E@QFN48 [CX4043]  
CY8CTMG200A@QFN32 [CX4015]  
CY8CTMG201A@QFN32 [CX4015]  
CY8CTMG240A@QFN32 [CX4015]  
CY8CTST200@QFN32 [CX4015]  
CY8CTST200A@QFN32 [CX4015]  
CY8CTST201A@QFN32 [CX4015]  
CY8CTST241A@QFN32 [CX4015]  
CY8CTST242@QFN32 [CX4015]  
CY8CTST242A@QFN32 [CX4015]

CY8C20437@MLF32 [CX4015]  
CY8C20447@MLF32 [CX4015]  
CY8C20467@MLF32 [CX4015]  
CY8C20497@MLF32 [CX4015]  
CY8C21434@QFN32 [CX4015]  
CY8C21634@QFN32 [CX4015]  
CY8CTMA140 [CX0001]  
CY8CTMA140@QFN48 [CX4043]  
CY8CTMA140E@QFN36 [CX4042]  
CY8CTMA300E@QFN36 [CX4042]  
CY8CTMA340@QFN36 [CX4042]  
CY8CTMA375@QFN36 [CX4042]  
CY8CTMA375E@QFN36 [CX4042]  
CY8CTMG200@QFN32 [CX4015]  
CY8CTMG201@QFN32 [CX4015]  
CY8CTMG240@QFN32 [CX4015]  
CY8CTST200@QFN24 [CX4012]  
CY8CTST200A@QFN24 [CX4012]  
CY8CTST201@QFN32 [CX4015]  
CY8CTST241@QFN32 [CX4015]  
CY8CTST242 [CX0001]  
CY8CTST242A [CX0001]  
EM78P468NBL@QFP64 [BBBB]

EM78P468NBQ@QFP44 [CX3003]  
EM78P468NBQ@QFP64A [CX3044]

EM78P468NBQ@QFP64 [CX3015]  
EM78P468NBQL@QFP44 [CX3046]

## GAMMA

### E (E) PROM/FRAM/NVRAM

GAMNXX001JF9TC@TSOP48 [CX1004-3]

## GATELEVEL

### E (E) PROM/FRAM/NVRAM

GM24LC02B [CX0001]  
GM24LC02B@TSSOP8 [CX1059]  
GM24LC04B@SOIC8 [CX1045]  
GM24LC08B [CX0001]  
GM24LC08B@TSSOP8 [CX1059]  
GM24LC16B@SOIC8 [CX1045]

GM24LC02B@SOIC8 [CX1045]  
GM24LC04B [CX0001]  
GM24LC04B@TSSOP8 [CX1059]  
GM24LC08B@SOIC8 [CX1045]  
GM24LC16B [CX0001]  
GM24LC16B@TSSOP8 [CX1059]

## GENCORE

### MICROCONTROLLER

GC87C520A0 [CX0001]  
GC87C520A0@TQFP44 [CX3003]  
GC87C520G0@PLCC44 [CX2044]  
GC89L541A0@LQFP44 [CX3002]  
GC89L541A0@MQFP44 [CX3066]  
GC89L541A0@QFN32 [CX4015]  
GC89L581A0@MLF32 [CX4015]  
GC89L581A0@PQFP44 [CX3066]  
GC89L591A0@LQFP44 [CX3002]  
GC89L591A0@MQFP44 [CX3066]  
GC89L591A0@QFN32 [CX4015]

GC87C520A0@PLCC44 [CX2044]  
GC87C520G0 [CX0001]  
GC87C520G0@TQFP44 [CX3003]  
GC89L541A0@MLF32 [CX4015]  
GC89L541A0@PQFP44 [CX3066]  
GC89L581A0@LQFP44 [CX3002]  
GC89L581A0@MQFP44 [CX3066]  
GC89L581A0@QFN32 [CX4015]  
GC89L591A0@MLF32 [CX4015]  
GC89L591A0@PQFP44 [CX3066]

## GENERAL(GI)

### E (E) PROM/FRAM/NVRAM

27256 [CX0001]  
27C128@PLCC32 [CX2032]  
27C256@PLCC32 [CX2032]  
27C513 [CX0001]  
27C64@PLCC32 [CX2032]  
27HC291 [CX0001]  
27HC641 [CX0001]  
27HC64L [CX0001]  
28C04A [CX0001]  
28C16 [CX0001]  
28C16F [CX0001]  
28C17F [CX0001]  
ER5911@SOIC8 [CX1045]  
GI5911@SOIC8 [CX1045]  
GI59C11@SOIC8 [CX1045]

27C128 [CX0001]  
27C256 [CX0001]  
27C512 [CX0001]  
27C64 [CX0001]  
27HC191 [CX0001]  
27HC64 [CX0001]  
27HC641L [CX0001]  
28C04 [CX0001]  
28C04F [CX0001]  
28C16A [CX0001]  
28C17 [CX0001]  
ER5911 [CX0001]  
GI5911 [CX0001]  
GI59C11 [CX0001]  
GI59C12 [CX0001]

GI59C12@SOIC8 [CX1045]

GR27C513 [CX0001]

## GENERALPLUS

### E (E) PROM/FRAM/NVRAM

GPR25L005E@SOP8 [CX1045#1]

GPR25L021B@SOP8 [CX1045#1]

GPR25L081B@SOP8 [CX1045#1]

GPR25L162B@SOP8 [CX1045#1]

GPR25L6404E@SOP16 [CX1033#1]

GPR25L6404E@SOP16(OTP) [CX1033#1]

GPR25L6404E@SOP8 [CX1044#1]

GPR25L011E@SOP8 [CX1045#1]

GPR25L041B@SOP8 [CX1045#1]

GPR25L1284E@SOP16 [CX1033#1]

GPR25L322B@SOP8 [CX1045#1]

GPR25L6404E@SOP8(OTP) [CX1044#1]

## GENERIC

### E (E) PROM/FRAM/NVRAM

27128(21V)

2716(25V) [CX0001]

2732(25V) [CX0001]

2732B(12.5V) [CX0001]

27512(21V) [CX0001]

2764A(12.5V) [CX0001]

27C128(21V) [CX0001]

27C256(12.5V) [CX0001]

27C512(12.5V) [CX0001]

27C64(21V) [CX0001]

27128A(12.5V) [CX0001]

27256(12.5V) [CX0001]

2732A(21V) [CX0001]

27512(12.5V) [CX0001]

2764(21V) [CX0001]

27C128(12.5V) [CX0001]

27C16(25V) [CX0001]

27C32(25V) [CX0001]

27C64(12.5V) [CX0001]

## GENITOP

### E (E) PROM/FRAM/NVRAM

GT16G80 [CX0001]

GT16G80@SOP8 [CX1044#1]

GT32G16 [CX0001]

GT32G16@SOP8 [CX1044#1]

GT32G40 [CX0001#1]

GT32G40@SOP8 [CX1044#1]

GT40G10 [CX0001]

GT40G10@SOP8 [CX1044#1]

GT64G80 [CX0001]

GT64G80@VDFN8-1 [CX4005#1]

GT16G80@SOP16 [CX1033#1]

GT16G80@VDFN8 [CX4006#1]

GT32G16@SOP16 [CX1033#1]

GT32G16@VDFN8 [CX4006#1]

GT32G40@SOP16 [CX1033#1]

GT32G40@VDFN8 [CX4005#1]

GT40G10@SOP16 [CX1033#1]

GT40G10@VDFN8 [CX4006#1]

GT64G80@SOP8 [CX1044#1]

GT64G80@VDFN8-2 [CX4006#1]

## GENUSION

### E (E) PROM/FRAM/NVRAM

G28FVW5121S1TE@TSOP56 [CX1055]

## GIANTEC

### E (E) PROM/FRAM/NVRAM



GT24C01 [CX0001]  
GT24C01@SOP8 [CX1045]  
GT24C01@TSSOP8 [CX1059]  
GT24C02@DFN8 [CX4047]  
GT24C02@SOP8 [CX1045]  
GT24C02@TSSOP8 [CX1059]  
GT24C04@DFN8 [CX1015]  
GT24C04@SOP8 [CX1045]  
GT24C04@TSSOP8 [CX1059]  
GT24C08@DFN8 [CX4047]  
GT24C08@SOP8 [CX1045]  
GT24C08@TSSOP8 [CX1059]  
GT24C128@SOP8 [CX1045]  
GT24C16 [CX0001]  
GT24C16@MSOP8 [CX1015]  
GT24C16@TSSOP8 [CX1059]  
GT24C256@SOP8 [CX1045]  
GT24C32 [CX0001]  
GT24C32@SOP8 [CX1045]  
GT24C32@UDFN8 [CX4047]  
GT24C64@MSOP8 [CX1015]  
GT24C64@TSSOP8 [CX1059]  
GT24E64@SOP8 [CX1045]  
GT25C01 [CX0001]  
GT25C01@TSSOP8 [CX1059]  
GT25C02@SOP8 [CX1045]  
GT25C04 [CX0001]  
GT25C04@TSSOP8  
GT25C08@SOIC8 [CX1045]  
GT25C128@SOIC8 [CX1045]  
GT25C16 [CX0001]  
GT25C16@TSSOP8 [CX1059]  
GT25C256@TSSOP8 [CX1059]  
GT25C32@SOIC8 [CX1045]  
GT25C64 [CX0001]  
GT25C64@TSSOP8 [CX1059]  
GT34C02@MSOP8 [CX1015]  
GT34C02@TSSOP8 [CX1059]  
GT93C46(08bit)@SOIC8 [CX1045]  
GT93C46(16bit) [CX0001]  
GT93C46(16bit)@TSSOP8 [CX1059]  
GT93C56(08bit)@SOIC8 [CX1045]  
GT93C56(16bit) [CX0001]  
GT93C56(16bit)@TSSOP8 [CX1059]  
GT93C66(08bit)@SOIC8 [CX1045]  
GT93C66(16bit) [CX0001]  
GT93C66(16bit)@TSSOP8 [CX1059]  
GT93C76(08bit)@SOIC8 [CX1045]  
GT93C76(16bit) [CX0001]  
GT93C76(16bit)@TSSOP8 [CX1059]  
GT93C86(08bit)@SOIC8 [CX1045]  
GT93C86(16bit) [CX0001]  
GT93C86(16bit)@TSSOP8 [CX1059]  
GT24C01@MSOP8 [CX1015]  
GT24C01@TSOT23 [CX1041]  
GT24C02 [CX0001]  
GT24C02@MSOP8 [CX1015]  
GT24C02@TSOT23 [CX1041]  
GT24C04 [CX0001]  
GT24C04@MSOP8 [CX1015]  
GT24C04@TSOT23 [CX1041]  
GT24C08 [CX0001]  
GT24C08@MSOP8 [CX1015]  
GT24C08@TSOT23 [CX1041]  
GT24C128 [CX0001]  
GT24C128@TSSOP14 [CX1000]  
GT24C16@DFN8 [CX1015]  
GT24C16@SOP8 [CX1045]  
GT24C256 [CX0001]  
GT24C256@TSSOP14 [CX1000]  
GT24C32@MSOP8 [CX1015]  
GT24C32@TSSOP8 [CX1059]  
GT24C64 [CX0001]  
GT24C64@SOP8 [CX1045]  
GT24C64@UDFN8 [CX4002]  
GT24E64@TSSOP8 [CX1059]  
GT25C01@SOP8 [CX1045]  
GT25C02 [CX0001]  
GT25C02@TSSOP8 [CX1059]  
GT25C04@SOP8 [CX1045]  
GT25C08 [CX0001]  
GT25C08@TSSOP8 [CX1059]  
GT25C128@TSSOP8 [CX1059]  
GT25C16@SOIC8 [CX1045]  
GT25C256@SOIC8 [CX1045]  
GT25C32 [CX0001]  
GT25C32@TSSOP8 [CX1059]  
GT25C64@SOIC8 [CX1045]  
GT34C02 [CX0001]  
GT34C02@SOP8 [CX1045]  
GT93C46(08bit) [CX0001]  
GT93C46(08bit)@TSSOP8 [CX1059]  
GT93C46(16bit)@SOIC8 [CX1045]  
GT93C56(08bit) [CX0001]  
GT93C56(08bit)@TSSOP8 [CX1059]  
GT93C56(16bit)@SOIC8 [CX1045]  
GT93C66(08bit) [CX0001]  
GT93C66(08bit)@TSSOP8 [CX1059]  
GT93C66(16bit)@SOIC8 [CX1045]  
GT93C76(08bit) [CX0001]  
GT93C76(08bit)@TSSOP8 [CX1059]  
GT93C76(16bit)@SOIC8 [CX1045]  
GT93C86(08bit) [CX0001]  
GT93C86(08bit)@TSSOP8 [CX1059]  
GT93C86(16bit)@SOIC8 [CX1045]

## GIGADEVICE

[E \(E\) PROM/FRAM/NVRAM](#)

GD25B128C [CX0001#1] GD25B128C@SOIC16 [CX1033#1]  
GD25B128C@SOIC8 [CX1044#1] GD25B128C@SON8 [CX4005#1]  
GD25B128C@TFBGA24[5\*5] [CX5157] GD25B128C@TFBGA24[6\*4] [CX5146]  
GD25B128C@VSON8 [CX1044#1] GD25B128C@WSON8 [CX4006#1]  
GD25B16B [CX0001] GD25B16B@SOP16 [CX1033#1]  
GD25B16B@SOP8[150mil] [CX1045#1] GD25B16B@SOP8[200mil] [CX1044#1]  
GD25B16B@TFBGA24 [CX5146] GD25B16B@WSON8 [CX4005#1]  
GD25B32B [CX0001] GD25B32B@SOP16 [CX1033#1]  
GD25B32B@SOP8 [CX1044#1] GD25B32B@TFBGA24 [CX5146]  
GD25B32B@WSON8 [CX4005#1] GD25B64B [CX0001]  
GD25B64B@SOP16 [CX1033#1] GD25B64B@SOP8 [CX1044#1]  
GD25B64B@TFBGA24 [CX5146] GD25B64B@WSON8 [CX4005#1]  
GD25D40 [CX0001] GD25D40@SOP8 [CX1044#1]  
GD25D80 [CX0001] GD25D80@SOP8 [CX1044#1]  
GD25E16 [CX0001] GD25E16@SOP8 [CX1044#1]  
GD25E40 [CX0001] GD25E40@SOP8 [CX1044#1]  
GD25E40@TSSOP8 [CX1045#1] GD25E64B@SOP8 [CX1044#1]  
GD25E80B [CX0001] GD25E80B@SOP8 [CX1044#1]  
GD25E80B@TSSOP8 [CX1045#1] GD25F40 [CX0001]  
GD25F40@SOP8 [CX1044#1] GD25F80 [CX0001]  
GD25F80@SOP8 [CX1044#1] GD25LQ128@SOP16 [CX1033#1]  
GD25LQ128@SOP8 [CX1044#1] GD25LQ128@WSON8 [CX4006#1]  
GD25LQ16@SOP8 [CX1044#1] GD25LQ16@TSOP8 [CX1044#1]  
GD25LQ16@USON8 [CX4005#1] GD25LQ16@WSON8 [CX4005#1]  
GD25LQ32@SOP8 [CX1044#1] GD25LQ32@WSON8 [CX4005#1]  
GD25LQ40@SOP8 [CX1045#1] GD25LQ40@TSOP8 [CX1059#3]  
GD25LQ40@USON8 [CX4005#1] GD25LQ40@WSON8 [CX4005#1]  
GD25LQ64@TSOP8 [CX1044#1] GD25LQ64@WSON8 [CX4005#1]  
GD25LQ64B@SOP16 [CX1033#1] GD25LQ64B@SOP8 [CX1044#1]  
GD25LQ64B@WSON8 [CX4005#1] GD25LQ80@SOP8 [CX1045#1]  
GD25LQ80@USON8 [CX4005#1] GD25LQ80@WSON8 [CX4005#1]  
GD25M21B@SOIC8 [CX1045#1] GD25M21B@TSSOP8 [CX1059#3]  
GD25M21B@USON8 [CX4002#1] GD25M41B@SOIC8 [CX1045#1]  
GD25M41B@TSSOP8 [CX1059#3] GD25M41B@USON8 [CX4002#1]  
GD25Q10 [CX0001] GD25Q10@SOP8(150 mil) [CX1045#1]  
GD25Q10@SOP8(200 mil) [CX1044#1] GD25Q10@USON8 [CX4002#1]  
GD25Q128B@SOP16 [CX1033#1] GD25Q128B@WSON8 [CX4006#1]  
GD25Q128C [CX0001] GD25Q128C@SOP16 [CX1033#1]  
GD25Q128C@SOP8 [CX1044#1] GD25Q128C@TFBGA24 [CX5146]  
GD25Q128C@TSOP8 [CX1044#1] GD25Q128C@WSON8 [CX4006#1]  
GD25Q16 [CX0001] GD25Q16@SOP8 [CX1044#1]  
GD25Q16B [CX0001] GD25Q16B@SOP8 [CX1044#1]  
GD25Q20 [CX0001] GD25Q20@SOP8(150 mil) [CX1045#1]  
GD25Q20@SOP8(200 mil) [CX1044#1] GD25Q20@USON8 [CX4002#1]  
GD25Q20B@SOIC8 [CX1045#1] GD25Q20B@TSSOP8 [CX1059#3]  
GD25Q20B@USON8 [CX4002#1] GD25Q21B@SOIC8 [CX1045#1]  
GD25Q21B@TSSOP8 [CX1059#3] GD25Q21B@USON8 [CX4002#1]  
GD25Q32 [CX0001]  
GD25Q32(4\*256 Security) [CX1044#1]  
GD25Q32@SOP8 [CX1044#1]  
GD25Q32@SOP8(4\*256 Security) [CX1044#1]  
GD25Q32B [CX0001] GD25Q32B@SOP8 [CX1044#1]  
GD25Q32B@TFBGA24 [CX5146] GD25Q40 [CX0001]  
GD25Q40@SOP8(150 mil) [CX1045#1] GD25Q40@SOP8(200 mil) [CX1044#1]  
GD25Q40@USON8 [CX4002#1] GD25Q40B@SOIC8 [CX1045#1]  
GD25Q40B@TSSOP8 [CX1059#3] GD25Q40B@USON8 [CX4002#1]  
GD25Q41B@SOIC8 [CX1045#1] GD25Q41B@TSSOP8 [CX1059#3]  
GD25Q41B@USON8 [CX4002#1] GD25Q512 [CX0001]  
GD25Q512@SOP8 [CX1045#1] GD25Q512@TSSOP8 [CX1059#3]

GD25Q512@USON8 [CX4002#1]  
GD25Q64B@SOP16 [CX1033#1]  
GD25Q64B@TFBGA24 [CX5146]  
GD25Q64B@WSON8[6\*5] [CX4005#1]  
GD25Q80 [CX0001]  
GD25Q80@SOP8(200 mil) [CX1044#1]  
GD25Q80B@SOP8(150 mil) [CX1045#1]  
GD25Q80B@SOP8(200 mil) [CX1044#1]  
GD25T80 [CX0001]  
GD25VQ21B@SOIC8 [CX1045#1]  
GD25VQ21B@USON8 [CX4002#1]  
GD25VQ41B@TSSOP8 [CX1059#3]  
GD29GL064CAB@FBGA48 [CX5002]  
GD29GL064CAB@FBGA48(SLOW) [CX5002]  
GD5F1GQ4UAYIG@QFN8  
MD25D16@SOP8(150 mil) [CX1044#1]  
MD25D20 [CX0001]  
MD25D20@SOP8(200 mil) [CX1044#1]  
MD25D40 [CX0001]  
MD25D40@SOP8(200 mil) [CX1044#1]  
MD25D80 [CX0001]  
MD25D80@SOP8(200 mil) [CX1044#1]  
S64M80GX@SOP16 [CX1033#1]  
S64M80GX@TFBGA24 [CX5146]

GD25Q64B [CX0001]  
GD25Q64B@SOP8 [CX1044#1]  
GD25Q64B@TSOP8 [CX1044#1]  
GD25Q64B@WSON8[6\*8] [CX4006#1]  
GD25Q80@SOP8(150 mil) [CX1045#1]  
GD25Q80B [CX0001]  
GD25T80@SOP8 [CX1044#1]  
GD25VQ21B@TSSOP8 [CX1059#3]  
GD25VQ41B@SOIC8 [CX1045#1]  
GD25VQ41B@USON8 [CX4002#1]  
MD25D16 [CX0001]  
MD25D16@SOP8(200 mil) [CX1045#1]  
MD25D20@SOP8(150 mil) [CX1045#1]  
MD25D20@USON8 [CX4002#1]  
MD25D40@SOP8(150 mil) [CX1045#1]  
MD25D40@USON8 [CX4002#1]  
MD25D80@SOP8(150 mil) [CX1045#1]  
S64M80GX [CX0001#1]  
S64M80GX@SOP8 [CX1044#1]  
S64M80GX@WSON8 [CX4006#1]

## MICROCONTROLLER

GD32F103C4@LQFP48 [CX3007]  
GD32F103C8@LQFP48 [CX3007]  
GD32F103R4@LQFP64 [CX3011]  
GD32F103R8@LQFP64 [CX3011]  
GD32F103T4@QFN36 [CX4029]  
GD32F103T8@QFN36 [CX4029]  
GD32F103V8@LQFP100 [CX3043]

GD32F103C6@LQFP48 [CX3007]  
GD32F103CB@LQFP48 [CX3007]  
GD32F103R6@LQFP64 [CX3011]  
GD32F103RB@LQFP64 [CX3011]  
GD32F103T6@QFN36 [CX4029]  
GD32F103TB@QFN36 [CX4029]  
GD32F103VB@LQFP100 [CX3043]

## GMT

### E (E) PROM/FRAM/NVRAM

AUO-G1422.29@TQFN32 [CX4015]

## MICROCONTROLLER

G1601A@QFN28 [CX4013]

## GOAL

### MICROCONTROLLER

VRS1000 [CX0001]  
VRS1000@TQFP44 [CX3003]  
VRS1050@PLCC44 [CX2044]  
VRS1100 [CX0001]  
VRS1100@TQFP44 [CX3003]  
VRS540@PLCC44 [CX2044]

VRS1000@PLCC44 [CX2044]  
VRS1050 [CX0001]  
VRS1050@TQFP44 [CX3003]  
VRS1100@PLCC44 [CX2044]  
VRS540 [CX0001]  
VRS540@TQFP44 [CX3003]

VRS550 [CX0001]  
VRS550@TQFP44 [CX3003]  
VRS560@PLCC44 [CX2044]  
VRS570 [CX0001]  
VRS570@TQFP44 [CX3003]  
VRS580@PLCC44 [CX2044]  
VRS700 [CX0001]  
VRS700@TQFP44 [CX3003]  
VRS900@PLCC44 [CX2044]

VRS550@PLCC44 [CX2044]  
VRS560 [CX0001]  
VRS560@TQFP44 [CX3003]  
VRS570@PLCC44 [CX2044]  
VRS580 [CX0001]  
VRS580@TQFP44 [CX3003]  
VRS700@PLCC44 [CX2044]  
VRS900 [CX0001]  
VRS900@TQFP44 [CX3003]

## GOULD

### PLD

PEEL153 [CX0001]  
PEEL18CV8J@PLCC20 [CX2020]  
PEEL18CV8S@SOIC20 [CX1033]  
PEEL253 [CX0001]

PEEL173 [CX0001]  
PEEL18CV8P [CX0001]  
PEEL18CV8T@TSOP20 [CX1000]  
PEEL273 [CX0001]

## GREEN-ENGINE

### E (E) PROM/FRAM/NVRAM

GE24C01 [CX0001]  
GE24C01@TSSOP8 [CX1059]  
GE24C02@SOP8 [CX1045]  
GE24C04 [CX0001]  
GE24C04@TSSOP8 [CX1059]

GE24C01@SOP8 [CX1045]  
GE24C02 [CX0001]  
GE24C02@TSSOP8 [CX1059]  
GE24C04@SOP8 [CX1045]

## GREENLIANT

### E (E) PROM/FRAM/NVRAM

GLS29SF020@PLCC32 [CX2032]  
GLS29SF040@PLCC32 [CX2032]  
GLS29VF020@PLCC32 [CX2032]  
GLS29VF040@PLCC32 [CX2032]  
GLS37VF010 [CX0001]  
GLS37VF010@VSOP32 [CX1003]  
GLS37VF020@PLCC32 [CX2032]  
GLS37VF040 [CX0001]  
GLS37VF040@VSOP32 [CX1003]  
GLS37VF512@PLCC32 [CX2032]  
SST36VF1601G@FBGA48 [CX5002]  
SST36VF1602G@FBGA48 [CX5002]  
SST36VF3203@FBGA48 [CX5002]  
SST36VF3204@FBGA48 [CX5002]

GLS29SF020@VSOP32 [CX1003]  
GLS29SF040@VSOP32 [CX1003]  
GLS29VF020@VSOP32 [CX1003]  
GLS29VF040@VSOP32 [CX1003]  
GLS37VF010@PLCC32 [CX2032]  
GLS37VF020 [CX0001]  
GLS37VF020@VSOP32 [CX1003]  
GLS37VF040@PLCC32 [CX2032]  
GLS37VF512 [CX0001]  
GLS37VF512@VSOP32 [CX1003]  
SST36VF1601G@TSOP48 [CX1004]  
SST36VF1602G@TSOP48 [CX1004]  
SST36VF3203@TSOP48 [CX1004]  
SST36VF3204@TSOP48 [CX1004]

## GREENWICH

### E (E) PROM/FRAM/NVRAM

GR27128 [CX0001]  
GR27512 [CX0001]

GR27256 [CX0001]  
GR2764 [CX0001]

# GTM

## E (E) PROM/FRAM/NVRAM

GP24BC01 [CX0001]	GP24BC01@SOP8 [CX1045]
GP24BC01@TSSOP8 [CX1059]	GP24BC02 [CX0001]
GP24BC02@SOP8 [CX1045]	GP24BC02@TSSOP8 [CX1059]
GP24BC04 [CX0001]	GP24BC04@SOP8 [CX1045]
GP24BC04@TSSOP8 [CX1059]	GP24BC08 [CX0001]
GP24BC08@SOP8 [CX1045]	GP24BC08@TSSOP8 [CX1059]
GP24BC16 [CX0001]	GP24BC16@SOP8 [CX1045]
GP24BC16@TSSOP8 [CX1059]	

# HAIER

## MICROCONTROLLER

HR6P58P1D1L [CX0001]	HR6P58P1D2L [CX0001]
HR6P58P1RL@SSOP10 [CX1026]	HR6P58P1S2L [CX1045]
HR6P58P1YL@SOP14 [CX1033]	HR6P59P2D2HL [CX0001]
HR6P59P2DHL [CX0001]	HR6P59P2DL [CX0001]
HR6P59P2RHL@SSOP10 [CX1026]	HR6P59P2S2HL [CX1044]
HR6P59P2SHL@SOP14 [CX1033]	HR6P59P2SL@SOP14 [CX1016]
HR6P59P2YHL [CX1045]	HR6P60P2D2HL [CX0001]
HR6P60P2DL [CX0001]	HR6P60P2DLA [CX0001]
HR6P60P2EL [CX0001]	HR6P60P2ELA [CX0001]
HR6P60P2RHL@SSOP20 [CX1000]	HR6P60P2RL@SSOP20 [CX1026]
HR6P60P2RLA@SSOP20 [CX1026]	HR6P60P2S1HL@SOP20 [CX1033]
HR6P60P2S2HL@SOP18 [CX1033]	HR6P60P2SL@SOP20 [CX1033]
HR6P60P2SLA@SOP20 [CX1033]	HR6P60P2XL@SOP18 [CX1033]
HR6P60P2XLA@SOP18 [CX1033]	HR6P60P2YL@SOP14 [CX1033]
HR6P60P2YLA@SOP14 [CX1033]	HR6P61P2D1L [CX0001]
HR6P61P2D2L [CX0001]	HR6P61P2D3L [CX0001]
HR6P61P2D4L [CX0001]	HR6P61P2S1L@SOP20 [CX1033]
HR6P61P2S2L@SOP18 [CX1033]	HR6P61P2S3L@SOP16 [CX1033]
HR6P61P2S4L@SOP14 [CX1033]	HR6P62P4D [CX0001]
HR6P62P4DH [CX0001]	HR6P62P4DHL [CX0001]
HR6P62P4DHL(INTOSC) [CX0001]	HR6P62P4DHL-D [CX0001]
HR6P62P4DHL-D(INTOSC) [CX0001]	
HR6P62P4NHL(INTOSC)@SOP20 [CX1026]	
HR6P62P4NHL@SSOP20 [CX1026]	
HR6P62P4NHLD(INTOSC)@SSOP20 [CX1026]	
HR6P62P4NHLD@SSOP20 [CX1026]	
HR6P62P4RHL(INTOSC)@SOP20 [CX1026]	
HR6P62P4RHL@SSOP20 [CX1026]	
HR6P62P4RHL-D(INTOSC)@SSOP20 [CX1026]	
HR6P62P4RHL-D@SSOP20 [CX1026]	HR6P62P4SH@SOP20 [CX1033]
HR6P62P4SHL(INTOSC)@SOP20 [CX1033]	
HR6P62P4SHL@SOP20 [CX1033]	
HR6P62P4SHLD(INTOSC)@SOP20 [CX1033]	
HR6P62P4SHLD@SOP20 [CX1033]	
HR6P62P4XHL(INTOSC)@SOP18 [CX1033]	
HR6P62P4XHL@SOP18 [CX1033]	
HR6P62P4XHL-D(INTOSC)@SOP18 [CX1033]	
HR6P62P4XHL-D@SOP18 [CX1033]	HR6P62P4YHL@SOP14 [CX1000]
HR6P62P4YHLD@SOP14 [CX1000]	HR6P67P4D [CX0001]
HR6P67P4DL [CX0001]	HR6P67P4DL-B [CX0001]

HR6P67P4DLR [CX0001] HR6P67P4DLRB [CX0001]  
HR6P67P4SL@SOP14 [CX1065] HR6P67P4SL-B@SOP14 [CX1033]  
HR6P67P4SLR@SOP14 [CX1065] HR6P67P4SLRB@SOP14 [CX1033]  
HR6P71F8D [CX0001] HR6P71F8D(BOREN) [CX0001]  
HR6P71F8D(BOREN)(ISP) [CX0001] HR6P71F8D(ISP) [CX0001]  
HR6P71F8D(REVERSE) [CX0001] HR6P71F8S(BOREN)@SOP20 [CX1033]  
HR6P71F8S(BOREN)@SOP20(ISP) [CX0001]  
HR6P71F8S(REVERSE)@SOP20 [CX1033]  
HR6P71F8S@SOP20 [CX1033] HR6P71F8S@SOP20(ISP) [CX0001]  
HR6P72P4D [CX0001] HR6P72P4DL [CX0001]  
HR6P72P4S@SOP28 [CX1033] HR6P72P4SL@SOP28 [CX1033]  
HR6P73P8DB [CX0001] HR6P73P8DBL [CX0001]  
HR6P73P8SB@SOP28 [CX1033] HR6P73P8SBL@SOP28 [CX1033]  
HR6P73PGD [CX0001] HR6P73PGDH [CX0001]  
HR6P73PGDHL [CX0001] HR6P73PGS@SOP28 [CX1033]  
HR6P73PGSH@SOP28 [CX1033] HR6P73PGSHL@SOP28 [CX1033]  
HR6P76PGD [CX0001] HR6P76PGDL [CX0001]  
HR6P76PGS@SOP28 [CX1033] HR6P76PGSL@SOP28 [CX1033]  
HR6P77PGD [CX0001] HR6P77PGDL [CX0001]  
HR6P77PGL@LQFP44 [CX3003] HR6P77PGLL@LQFP44 [CX3005]  
HR6P78P4SL@SOP32 [CX1069] HR6P90FGD [CX0001]  
HR6P90FGD(ISP) [CX0001] HR6P90FGS@SOP28 [CX1033]  
HR6P90FGS@SOP28(ISP) [CX0001] HR6P90FHD [CX0001]  
HR6P90FHD(ISP) [CX0001] HR6P90FHS@SOP28 [CX1033]  
HR6P90FHS@SOP28(ISP) [CX0001] HR6P91FGS@SOP32 [CX1069]  
HR6P91FGS@SOP32(ISP) [CX0001] HR6P91FHS@SOP32 [CX1069]  
HR6P91FHS@SOP32(ISP) [CX0001] HR6P92FGD [CX0001]  
HR6P92FGD(ISP) [CX0001] HR6P92FGL@LQFP44 [CX3003]  
HR6P92FGL@LQFP44(ISP) [CX0001] HR6P92FHD [CX0001]  
HR6P92FHD(ISP) [CX0001] HR6P92FHL@LQFP44 [CX3003]  
HR6P92FHL@LQFP44(ISP) [CX0001] HR6P95F8D [CX0001]  
HR6P95F8D(ISP) [CX0001] HR6P95F8S@SOP28  
HR6P95F8S@SOP28(ISP) [CX0001] HR6P97FGD [CX0001]  
HR6P97FGD(ISP) [CX0001] HR6P97FGD-E [CX0001]  
HR6P97FGD-E(ISP) [CX0001] HR6P97FGS@SOP28 [CX1033]  
HR6P97FGS@SOP28(ISP) [CX0001] HR6P97FGS-E@SOP28 [CX1033]  
HR6P97FGS-E@SOP28(ISP) [CX0001] HR6P98FGD [CX0001]  
HR6P98FGD(ISP) [CX0001] HR6P98FGD-E [CX0001]  
HR6P98FGD-E(ISP) [CX0001] HR6P98FGL@LQFP44 [CX3003]  
HR6P98FGL@LQFP44(ISP) [CX0001] HR6P98FGL-E@LQFP44 [CX3003]  
HR6P98FGL-E@LQFP44(ISP) [CX0001] HR7P164P4D1L [CX0001]  
HR7P164P4D2L [CX0001] HR7P164P4D3L [CX0001]  
HR7P164P4D4L [CX0001] HR7P164P4RL@SSOP20 [CX1000]  
HR7P164P4S1L@SOP20 [CX1033] HR7P164P4S2L@SOP18 [CX1033]  
HR7P164P4S3L@SOP16 [CX1033] HR7P164P4S4L@SOP14 [CX1033]  
HR7P171F8D1 [CX0001] HR7P171F8D2 [CX0001]  
HR7P171F8D3 [CX0001] HR7P171F8D4 [CX0001]  
HR7P171F8S1@SOP20 [CX1033] HR7P171F8S2@SOP18 [CX1033]  
HR7P171F8S3@SOP16 [CX1033] HR7P171F8S4@SOP14 [CX1030]  
HR7P187F4D1 [CX0001] HR7P187F4D2 [CX0001]  
HR7P187F4S1@SOP14 [CX1030] HR7P187F4S2@SOP8 [CX1030]  
HR7P193FGD1 [CX0001] HR7P193FGS@LQFP44 [CX3005]  
HR7P193FGS@SOP28 [CX1033] HR7P193FGS@SOP32 [CX1069]  
HR7P193FGV [CX0001] HR7P194FGD1 [CX0001]  
HR7P194FGS@LQFP44 [CX3005] HR7P194FGS@SOP28 [CX1033]  
HR7P194FGS@SOP32 [CX1069] HR7P194FGV [CX0001]  
HR7P195F8D1 [CX0001] HR7P195F8D2 [CX0001]  
HR7P195F8R@SSOP20 [CX1074] HR7P195F8S@SOP28 [CX1033]  
HR7P195F8S2@SOP20 [CX1033] HR7P195F8S3@SOP32 [CX1069]

HR7P195F8V [CX0001]  
HR7P195FGD2 [CX0001]  
HR7P195FGS@SOP28 [CX1033]  
HR7P195FGS3@SOP32 [CX1069]  
HR7P90FHD [CX0001]  
HR7P90FJD [CX0001]  
HR7P91FHL@LQFP32 [CX3001]  
HR7P91FHV [CX0001]  
HR7P91FJS@SOP32 [CX1069]  
HR7P92FHL@LQFP44 [CX3005]  
HR7T46P8V@SDIP42 [CX0042]  
MC9S08AC16CFG [CX3107-1]  
MC9S08AC16CFJ@QFP32 [CX3109-1]  
MC9S08AC16MFG [CX3107-1]  
MC9S08AC16MFJ@QFP32 [CX3109-1]  
MC9S08AC16VFG [CX3107-1]  
MC9S08AC16VFJ@QFP32 [CX3109-1]  
MC9S08AC32CFG [CX3107-1]  
MC9S08AC32CFJ@QFP32 [CX3109-1]  
MC9S08AC32MFG [CX3107-1]  
MC9S08AC32MFJ@QFP32 [CX3109-1]  
MC9S08AC32VFG [CX3107-1]  
MC9S08AC32VFJ@QFP32 [CX3109-1]  
MC9S08AC48CFG [CX3107-1]  
MC9S08AC48CFJ@QFP32 [CX3109-1]  
MC9S08AC48MFG [CX3107-1]  
MC9S08AC48MFJ@QFP32 [CX3109-1]  
MC9S08AC48VFG [CX3107-1]  
MC9S08AC48VFJ@QFP32 [CX3109-1]  
MC9S08AC60CFG [CX3107-1]  
MC9S08AC60CFJ@QFP32 [CX3109-1]  
MC9S08AC60MFG [CX3107-1]  
MC9S08AC60MFJ@QFP32 [CX3109-1]  
MC9S08AC60VFG [CX3107-1]  
MC9S08AC60VFJ@QFP32 [CX3109-1]  
MC9S08AC8CFG [CX3107-1]  
MC9S08AC8CFJ@QFP32 [CX3109-1]  
MC9S08AC8MFG [CX3107-1]  
MC9S08AC8MFJ@QFP32 [CX3109-1]  
MC9S08AC8VFG [CX3107-1]  
MC9S08AC8VFJ@QFP32 [CX3109-1]  
MC9S08AW16CFG [CX3107-1]  
MC9S08AW16MFG [CX3107-1]  
MC9S08AW16VFG [CX3107-1]  
MC9S08AW32CFG [CX3107-1]  
MC9S08AW32MFG [CX3107-1]  
MC9S08AW32VFG [CX3107-1]  
MC9S08AW48CFG [CX3107-1]  
MC9S08AW48MFG [CX3107-1]  
MC9S08AW48VFG [CX3107-1]  
MC9S08AW60CFG [CX3107-1]  
MC9S08AW60MFG [CX3107-1]  
MC9S08AW60VFG [CX3107-1]  
S9S08AW16ACLM@QFP32 [CX3109-1]  
S9S08AW16AAML@QFP32 [CX3109-1]  
S9S08AW16AVLM@QFP32 [CX3109-1]  
S9S08AW8ACLM@QFP32 [CX3109-1]  
S9S08AW8AAML@QFP32 [CX3109-1]  
S9S08AW8AVLM@QFP32 [CX3109-1]

HR7P195FGD1 [CX0001]  
HR7P195FGR@SSOP20 [CX0001]  
HR7P195FGS2@SOP20 [CX1033]  
HR7P195FGV [CX0001]  
HR7P90FHS@SOP28 [CX1033]  
HR7P90FJS@SOP28 [CX1033]  
HR7P91FHS@SOP32 [CX1069]  
HR7P91FJL@LQFP32 [CX3001]  
HR7P91FJV [CX0001]  
HR7P92FJL@LQFP44 [CX3005]  
HR7T47P8L@LQFP44 [CX3003]  
MC9S08AC16CFGE [CX3107-1]  
MC9S08AC16CFJE@QFP32 [CX3109-1]  
MC9S08AC16MFGE [CX3107-1]  
MC9S08AC16MFJE@QFP32 [CX3109-1]  
MC9S08AC16VFGE [CX3107-1]  
MC9S08AC16VFJE@QFP32 [CX3109-1]  
MC9S08AC32CFGE [CX3107-1]  
MC9S08AC32CFJE@QFP32 [CX3109-1]  
MC9S08AC32MFGE [CX3107-1]  
MC9S08AC32MFJE@QFP32 [CX3109-1]  
MC9S08AC32VFGE [CX3107-1]  
MC9S08AC32VFJE@QFP32 [CX3109-1]  
MC9S08AC48CFGE [CX3107-1]  
MC9S08AC48CFJE@QFP32 [CX3109-1]  
MC9S08AC48MFGE [CX3107-1]  
MC9S08AC48MFJE@QFP32 [CX3109-1]  
MC9S08AC48VFGE [CX3107-1]  
MC9S08AC48VFJE@QFP32 [CX3109-1]  
MC9S08AC60CFGE [CX3107-1]  
MC9S08AC60CFJE@QFP32 [CX3109-1]  
MC9S08AC60MFGE [CX3107-1]  
MC9S08AC60MFJE@QFP32 [CX3109-1]  
MC9S08AC60VFGE [CX3107-1]  
MC9S08AC60VFJE@QFP32 [CX3109-1]  
MC9S08AC8CFGE [CX3107-1]  
MC9S08AC8CFJE@QFP32 [CX3109-1]  
MC9S08AC8MFGE [CX3107-1]  
MC9S08AC8MFJE@QFP32 [CX3109-1]  
MC9S08AC8VFGE [CX3107-1]  
MC9S08AC8VFJE@QFP32 [CX3109-1]  
MC9S08AW16CFGE [CX3107-1]  
MC9S08AW16MFGE [CX3107-1]  
MC9S08AW16VFGE [CX3107-1]  
MC9S08AW32CFGE [CX3107-1]  
MC9S08AW32MFGE [CX3107-1]  
MC9S08AW32VFGE [CX3107-1]  
MC9S08AW48CFGE [CX3107-1]  
MC9S08AW48MFGE [CX3107-1]  
MC9S08AW48VFGE [CX3107-1]  
MC9S08AW60CFGE [CX3107-1]  
MC9S08AW60MFGE [CX3107-1]  
MC9S08AW60VFGE [CX3107-1]  
S9S08AW16ACLS [CX3107-1]  
S9S08AW16AMLS [CX3107-1]  
S9S08AW16AVLS [CX3107-1]  
S9S08AW8ACLS [CX3107-1]  
S9S08AW8AMLS [CX3107-1]  
S9S08AW8AVLS [CX3107-1]

SH67P33 [CX0001]  
SH67P33@SSOP20 [CX1067]  
SH67P33C@SOIC20 [CX1033]

SH67P33@SOIC20 [CX1033]  
SH67P33C [CX0001]  
SH67P33C@SSOP20 [CX1067]

## HARRIS

### E (E) PROM/FRAM/NVRAM

HM-6616 [CX0001]

M1-6617/883 [CX0001]

### BPROM

7610A [CX0001]

7611A [CX0001]

### DRAM & SRAM

HM65642 [CX0001]

HM65642@TSOP28 [CX1001]

## HITACHI

### E (E) PROM/FRAM/NVRAM

HN27128AG [CX0001]  
HN27256G [CX0001]  
HN27512G [CX0001]  
HN27C101AG [CX0001]  
HN27C101G [CX0001]  
HN27C1024HG [CX0001]  
HN27C256AG [CX0001]  
HN27C256G [CX0001]  
HN27C301AG [CX0001]  
HN27C301G [CX0001]  
HN27C4000FP [CX0001]  
HN27C4001 [CX0001]  
HN27C4001G [CX0001]  
HN27C4096A@PLCC44 [CX2044]  
HN27C4096FP@PLCC44 [CX2044]  
HN27C4096G@PLCC44 [CX2044]  
HN27C512G@PLCC32 [CX2032]  
HN28F101 [CX0001]  
HN28F101(REVERSE)@TSOP32 [CX1002]  
HN28F101@PLCC32 [CX2032]  
HN28F101@TSOP32 [CX1002]  
HN462732G [CX0001]  
HN48016P  
HN4827128P [CX0001]  
HN482764G [CX0001]  
HN58064(FP)@SOIC28 [CX1033]  
HN58C1001(FP)@SSOP32 [CX1020]  
HN58C1001(T)@VSOP32 [CX1003]  
HN58C256A(P) [CX0001]  
HN58C257A(T)@TSOP32 [CX1032]  
HN58C65(P) [CX0001]  
HN58V24256@SOIC8 [CX1045]  
HN58V24512 [CX0001]

HN27128AP [CX0001]  
HN27256P [CX0001]  
HN27512P [CX0001]  
HN27C101AP [CX0001]  
HN27C101P [CX0001]  
HN27C1024HG@PLCC44 [CX2044]  
HN27C256FP [CX0001]  
HN27C256HG [CX0001]  
HN27C301AP [CX0001]  
HN27C301P [CX0001]  
HN27C4000G [CX0001]  
HN27C4001@TSOP32 [CX1002]  
HN27C4096A [CX0001]  
HN27C4096FP [CX0001]  
HN27C4096G [CX0001]  
HN27C512G [CX0001]  
HN27C64G [CX0001]  
HN28F101@SOP32 [CX1019]  
HN462716G [CX0001]  
HN48016  
HN4827128G [CX0001]  
HN482732AG [CX0001]  
HN482764P [CX0001]  
HN58064(P) [CX0001]  
HN58C1001(P) [CX0001]  
HN58C256A(FP)@SOP28 [CX1033]  
HN58C256A(T)@TSOP28 [CX1024]  
HN58C65(FP)@SOIC28 [CX1033]  
HN58V24256 [CX0001]  
HN58V24256@TSSOP14 [CX1000]  
HN58V24512@SOIC8 [CX1045]



HN58V256A [CX0001]	HN58V256A@TSOP28 [CX1024]
HN58V65A [CX0001]	HN58V65A@SOIC28 [CX1064]
HN58V65A@TSOP28 [CX1024]	HN58V66A [CX0001]
HN58V66A@SOIC28 [CX1033]	HN58V66A@TSOP28 [CX1024]
HN58W241000 [CX0001]	
HN58W241000@SOIC8[150mil] [CX1045]	
HN58W241000@SOIC8[200mil] [CX1044]	
HN58X2402 [CX0001]	HN58X2402@SOIC8 [CX1045]
HN58X2402@TSSOP8 [CX1059]	HN58X2404 [CX0001]
HN58X2404@SOIC8 [CX1045]	HN58X2404@TSSOP8 [CX1059]
HN58X2408 [CX0001]	HN58X2408@SOIC8 [CX1045]
HN58X2408@TSSOP8 [CX1059]	HN58X24128 [CX0001]
HN58X24128@SOIC8 [CX1045]	HN58X2416 [CX0001]
HN58X2416@SOIC8 [CX1045]	HN58X2416@TSSOP8 [CX1059]
HN58X24256 [CX0001]	HN58X24256@SOIC8 [CX1045]
HN58X2432 [CX0001]	HN58X2432@SOIC8 [CX1045]
HN58X2432@TSSOP8 [CX1059]	HN58X24512 [CX0001]
HN58X24512@SOIC8 [CX1045]	HN58X2464 [CX0001]
HN58X2464@SOIC8 [CX1045]	HN58X2464@TSSOP8 [CX1059]
HN58X2502@SOIC8 [CX1045]	HN58X2502@TSSOP8 [CX1059]
HN58X2504@SOIC8 [CX1045]	HN58X2504@TSSOP8 [CX1059]
HN58X25128@SOIC8 [CX1045]	HN58X25128@TSSOP14 [CX1000]
HN58X25256@SOIC8 [CX1045]	HN58X25256@TSSOP14 [CX1000]
HN58X2532@SOIC8 [CX1045]	HN58X2532@TSSOP8 [CX1059]
HN58X2564@SOIC8 [CX1045]	HN58X2564@TSSOP8 [CX1059]
HT29VB800@TSOP48 [CX1043]	HT29VT800@TSOP48 [CX1043]
HT29WB800@TSOP48 [CX1043]	HT29WT800@TSOP48 [CX1043]

#### DRAM & SRAM

HM62256 [CX0001]	HM62256@TSOP28 [CX1001]
HM62256B [CX0001]	HM62256B@TSOP28 [CX1001]
HM6264A [CX0001]	HM6264A@TSOP28 [CX1001]
HM628128 [CX0001]	HM628128@TSOP32 [CX1002]
HM628128A [CX0001]	HM628128A@TSOP32 [CX1002]
HM62832 [CX0001]	HM62832@TSOP28 [CX1001]
HM62832H [CX0001]	HM62832H@TSOP28 [CX1001]
HM628512 [CX0001]	HM628512@TSOP32 [CX1002]
HM65256B [CX0001]	HM65256B@TSOP28 [CX1001]
HM658128 [CX0001]	HM658128@TSOP32 [CX1002]
HM66204 [CX0001]	HM66204@TSOP32 [CX1002]

#### MICROCONTROLLER

HD63701V0C [CX0001]	HD63701V0P [CX0001]
HD63701X0C@SDIP64 [CX0064]	HD63701X0P@SDIP64 [CX0064]
HD63701Y0 [CX0001]	HD63701Y0C [CX0001]
HD63701Y0C@SDIP64 [CX0064]	HD63701Y0P@SDIP64 [CX0064]
HD63705V0 [CX0001]	HD63705V0C [CX0001]
HD637A01V0C [CX0001]	HD637A01V0P [CX0001]
HD637A01X0C@SDIP64 [CX0064]	HD637A01X0P@SDIP64 [CX0064]
HD637A01Y0C@SDIP64 [CX0064]	HD637A01Y0P@SDIP64 [CX0064]
HD637A05V0 [CX0001]	HD637A05V0C [CX0001]
HD637B01V0C [CX0001]	HD637B01V0P [CX0001]
HD637B01X0C@SDIP64 [CX0064]	HD637B01X0P@SDIP64 [CX0064]
HD637B01Y0C@SDIP64 [CX0064]	HD637B01Y0P@SDIP64 [CX0064]
HD637B05V0 [CX0001]	HD637B05V0C [CX0001]
HD6473032F@QFP80 [CX3018]	HD6473032TF@QFP80 [CX3016]

HD6473334YCP@PLCC84 [CX2084]  
HD6473334YTF@QFP80 [CX3016]  
HD6473337YCP@PLCC84 [CX2084]  
HD6473644RH@QFP64 [CX3014]  
HD64738024H@QFP80 [CX3018]  
HD6475368CG@PLCC84 [CX2084]  
HD6475368F@QFP80 [CX3018]  
HD6475368RCP@PLCC84 [CX2084]  
HD6475368SCG@PLCC84 [CX2084]  
HD6475368SF@QFP80 [CX3018]  
HD64F2110BTE@QFP100 [CX3021]  
HD64F2110BVTE@QFP100 [CX3021]  
HD64F2132RTF10@QFP80 [CX3016]  
HD64F2132RVTF10@QFP80 [CX3016]  
HD64F2134ATF10@QFP80 [CX3016]  
HD64F2134AVTF10@QFP80 [CX3016]  
HD64F2134TF10@QFP80 [CX3016]  
HD64F2134VTF10@QFP80 [CX3016]  
HD64F2138ATF10@QFP80 [CX3016]  
HD64F2138AVTF10@QFP80 [CX3016]  
HD64F2138TF10@QFP80 [CX3016]  
HD64F2138VTF10@QFP80 [CX3016]  
HD64F2140BVTE10@QFP100 [CX3021]  
HD64F2141BVTE10@QFP100 [CX3021]  
HD64F2142RTE20@QFP100 [CX3021]  
HD64F2142RVTE10@QFP100 [CX3021]  
HD64F2144ATE20@QFP100 [CX3021]  
HD64F2144AVTE10@QFP100 [CX3021]  
HD64F2144TE20@QFP100 [CX3021]  
HD64F2144VTE10@QFP100 [CX3021]  
HD64F2145BVTE10@QFP100 [CX3021]  
HD64F2147ATE20@QFP100 [CX3021]  
HD64F2147AVTE10@QFP100 [CX3021]  
HD64F2147NTE20@QFP100 [CX3021]  
HD64F2147NVTE10@QFP100 [CX3021]  
HD64F2148ATE20@QFP100 [CX3021]  
HD64F2148AVTE10@QFP100 [CX3021]  
HD64F2148BTE20@QFP100 [CX3021]  
HD64F2148BVTE10@QFP100 [CX3021]  
HD64F2148TE20@QFP100 [CX3021]  
HD64F2148VTE10@QFP100 [CX3021]  
HD64F2149YTE20@QFP100 [CX3021]  
HD64F2149YVTE10@QFP100 [CX3021]  
HD64F2218UTF@QFP100 [CX3071]  
HD64F2238BF@PQFP100 [CX3022]  
HD64F2238BTE@TQFP100 [CX3043]  
HD64F2238RF@PQFP100 [CX3022]  
HD64F2238RTE@TQFP100 [CX3043]  
HD64F2239F@PQFP100 [CX3022]  
HD64F2239TE@TQFP100 [CX3043]  
HD64F2258F@PQFP100 [CX3022]  
HD64F2258TE@TQFP100 [CX3043]  
HD64F2265TE@TQFP100 [CX3043]  
HD64F2266FA@TQFP100 [CX3043]  
HD64F2266TF@TQFP100 [CX3071]  
HD64F2268TE@TQFP100 [CX3043]  
HD64F2280F20B@QFP100 [CX3022]  
HD64F2282F20@QFP100 [CX3022]  
HD64F2314VTE@QFP100 [CX3043]

HD6473334YF@QFP80 [CX3018]  
HD6473337YCG@PLCC84 [CX2084]  
HD6473644H@QFP64 [CX3014]  
HD64738024F@PQFP80 [CX3019]  
HD64738024W@QFP80 [CX3016]  
HD6475368CP@PLCC84 [CX2084]  
HD6475368RCG@PLCC84 [CX2084]  
HD6475368RF@QFP80 [CX3018]  
HD6475368SCP@PLCC84 [CX2084]  
HD64F2110BFA@QFP100 [CX3021]  
HD64F2110BVFA@QFP100 [CX3021]  
HD64F2132RFA20@QFP80 [CX3018]  
HD64F2132RVFA10@QFP80 [CX3018]  
HD64F2134AFA20@QFP80 [CX3018]  
HD64F2134AVFA10@QFP80 [CX3018]  
HD64F2134FA20@QFP80 [CX3018]  
HD64F2134VFA10@QFP80 [CX3018]  
HD64F2138AFA20@QFP80 [CX3018]  
HD64F2138AVFA10@QFP80 [CX3018]  
HD64F2138FA20@QFP80 [CX3018]  
HD64F2138VFA10@QFP80 [CX3018]  
HD64F2140BVFA10@QFP100 [CX3021]  
HD64F2141BVFA10@QFP100 [CX3021]  
HD64F2142RFA20@QFP100 [CX3021]  
HD64F2142RVFA10@QFP100 [CX3021]  
HD64F2144AFA20@QFP100 [CX3021]  
HD64F2144AVFA10@QFP100 [CX3021]  
HD64F2144FA20@QFP100 [CX3021]  
HD64F2144VFA10@QFP100 [CX3021]  
HD64F2145BVFA10@QFP100 [CX3021]  
HD64F2147AFA20@QFP100 [CX3021]  
HD64F2147AVFA10@QFP100 [CX3021]  
HD64F2147NFA20@QFP100 [CX3021]  
HD64F2147NVFA10@QFP100 [CX3021]  
HD64F2148AFA20@QFP100 [CX3021]  
HD64F2148AVFA10@QFP100 [CX3021]  
HD64F2148BFA20@QFP100 [CX3021]  
HD64F2148BVFA10@QFP100 [CX3021]  
HD64F2148FA20@QFP100 [CX3021]  
HD64F2148VFA10@QFP100 [CX3021]  
HD64F2149YFA20@QFP100 [CX3021]  
HD64F2149YVFA10@QFP100 [CX3021]  
HD64F2218TF@QFP100 [CX3071]  
HD64F2238ATE@TQFP100 [CX3043]  
HD64F2238BFA@QFP100 [CX3043]  
HD64F2238BTF@TQFP100 [CX3071]  
HD64F2238RFA@QFP100 [CX3043]  
HD64F2238RTF@TQFP100 [CX3071]  
HD64F2239F@QFP100 [CX3043]  
HD64F2239TF@TQFP100 [CX3071]  
HD64F2258FA@QFP100 [CX3043]  
HD64F2265FA@TQFP100 [CX3043]  
HD64F2265TF@TQFP100 [CX3071]  
HD64F2266TE@TQFP100 [CX3043]  
HD64F2268FA@TQFP100 [CX3043]  
HD64F2268TF@TQFP100 [CX3071]  
HD64F2280F20RB@QFP100 [CX3022]  
HD64F2314VF@PQFP100 [CX3022]  
HD64F2315VF@PQFP100 [CX3022]

HD64F2315VTE@QFP100 [CX3043] HD64F2317VF@PQFP100 [CX3022]  
HD64F2317VTE@QFP100 [CX3043] HD64F2317VTF@QFP100 [CX3043]  
HD64F2318VF@PQFP100 [CX3022] HD64F2318VTE@QFP100 [CX3043]  
HD64F2318VTF@QFP100 [CX3043] HD64F2319EVF@PQFP100 [CX3022]  
HD64F2319EVTE@QFP100 [CX3043] HD64F2319VF@PQFP100 [CX3022]  
HD64F2319VTE@QFP100 [CX3043] HD64F2357TE@QFP120 [CX3027]  
HD64F2612FA20@QFP80 [CX3018] HD64F2615F20@QFP80 [CX3018]  
HD64F2615F24@QFP80 [CX3018] HD64F3024F@TQFP100 [CX3021]  
HD64F3024FP@PQFP100 [CX3022] HD64F3024TE@TQFP100 [CX3021]  
HD64F3026F@QFP100 [CX3021] HD64F3026FP@PQFP100 [CX3022]  
HD64F3026TE@TQFP100 [CX3021] HD64F3029F@QFP100 [CX3043]  
HD64F3029TE@TQFP100 [CX3043] HD64F3039F@QFP80 [CX3018]  
HD64F3039TE@TQFP80 [CX3016] HD64F3039VF@QFP80 [CX3018]  
HD64F3039VTE@TQFP80 [CX3016] HD64F3048BF@TQFP100 [CX3021]  
HD64F3048BTE@TQFP100 [CX3021] HD64F3048BVF@TQFP100 [CX3021]  
HD64F3048BVTE@TQFP100 [CX3021] HD64F3048F@TQFP100 [CX3021]  
HD64F3048TF@TQFP100 [CX3021] HD64F3048VF@TQFP100 [CX3021]  
HD64F3048VTF@TQFP100 [CX3021] HD64F3052BF@TQFP100 [CX3021]  
HD64F3052BTE@TQFP100 [CX3021] HD64F3052BVF@TQFP100 [CX3021]  
HD64F3052BVTE@TQFP100 [CX3021] HD64F3052F@TQFP100 [CX3021]  
HD64F3052TE@TQFP100 [CX3021] HD64F3062BF@TQFP100 [CX3021]  
HD64F3062BFP@PQFP100 [CX3022] HD64F3062BTE@TQFP100 [CX3021]  
HD64F3062F@TQFP100 [CX3021] HD64F3062FP@PQFP100 [CX3022]  
HD64F3062RF@TQFP100 [CX3021] HD64F3062RFP@PQFP100 [CX3022]  
HD64F3062RTE@TQFP100 [CX3021] HD64F3062RVF@TQFP100 [CX3021]  
HD64F3062RVFP@PQFP100 [CX3022] HD64F3062RVTE@TQFP100 [CX3021]  
HD64F3062TE@TQFP100 [CX3021] HD64F3062VF@TQFP100 [CX3021]  
HD64F3062VFP@TQFP100 [CX3022] HD64F3062VTE@TQFP100 [CX3021]  
HD64F3064BF@TQFP100 [CX3021] HD64F3064BFP@PQFP100 [CX3022]  
HD64F3064BTE@TQFP100 [CX3021] HD64F3064F@TQFP100 [CX3021]  
HD64F3064FP@PQFP100 [CX3022] HD64F3064TE@TQFP100 [CX3021]  
HD64F3067F@TQFP100 [CX3021] HD64F3067FP@PQFP100 [CX3022]  
HD64F3067RF@TQFP100 [CX3021] HD64F3067RFP@PQFP100 [CX3022]  
HD64F3067RTE@TQFP100 [CX3021] HD64F3067RVF@TQFP100 [CX3021]  
HD64F3067RVFP@PQFP100 [CX3022] HD64F3067RVTE@TQFP100 [CX3021]  
HD64F3067TE@TQFP100 [CX3021] HD64F3067VF@TQFP100 [CX3021]  
HD64F3067VFP@TQFP100 [CX3022] HD64F3067VTE@TQFP100 [CX3021]  
HD64F3068F@TQFP100 [CX3021] HD64F3068TE@TQFP100 [CX3021]  
HD64F3069F@TQFP100 [CX3043] HD64F3069TE@TQFP100 [CX3043]  
HD64F3334YCP@PLCC84 [CX2084] HD64F3334YF@TQFP80 [CX3018]  
HD64F3334YFLH@TQFP80 [CX3018] HD64F3334YTF@TQFP80 [CX3016]  
HD64F3334YTF@TQFP80 [CX3016] HD64F3337YCP@PLCC84 [CX2084]  
HD64F3337YF@TQFP80 [CX3018] HD64F3337YFLH@TQFP80 [CX3018]  
HD64F3337YTF@TQFP80 [CX3016] HD64F3337YTF@TQFP80 [CX3016]  
HD64F3394YCP@PLCC84 [CX2084] HD64F3394YF@TQFP80 [CX3018]  
HD64F3394YFLH@TQFP80 [CX3018] HD64F3394YTF@TQFP80 [CX3016]  
HD64F3394YTF@TQFP80 [CX3016] HD64F3397CP@PLCC84 [CX2084]  
HD64F3397F@TQFP80 [CX3018] HD64F3397FLH@TQFP80 [CX3018]  
HD64F3397TF@TQFP80 [CX3016] HD64F3397TFLH@TQFP80 [CX3016]  
HD64F3434F@TQFP100 [CX3021] HD64F3434FLH@TQFP100 [CX3021]  
HD64F3434TF@TQFP100 [CX3021] HD64F3434TFLH@TQFP100 [CX3021]  
HD64F3437F@TQFP100 [CX3021] HD64F3437FLH@TQFP100 [CX3021]  
HD64F3437TF@TQFP100 [CX3021] HD64F3437TFLH@TQFP100 [CX3021]  
HD64F36012FP@QFP64 [CX3011] HD64F36012FT@QFN48 [CX4021]  
HD64F36012FX@QFP48 [CX3008] HD64F36012FY@QFP48 [CX3007]  
HD64F36012GFP@QFP64 [CX3011] HD64F36012GFT@QFN48 [CX4021]  
HD64F36012GFX@QFP48 [CX3008] HD64F36012GFY@QFP48 [CX3007]  
HD64F36014FP@QFP64 [CX3011] HD64F36014FT@QFN48 [CX4021]  
HD64F36014FX@QFP48 [CX3008] HD64F36014FY@QFP48 [CX3007]

HD64F36014GFP@QFP64 [CX3011]  
HD64F36014GFX@QFP48 [CX3008]  
HD64F36022FP@QFP64 [CX3011]  
HD64F36022FX@QFP48 [CX3008]  
HD64F36022GFP@QFP64 [CX3011]  
HD64F36022GFX@QFP48 [CX3008]  
HD64F36024FP@QFP64 [CX3011]  
HD64F36024FX@QFP48 [CX3008]  
HD64F36024GFP@QFP64 [CX3011]  
HD64F36024GFX@QFP48 [CX3008]  
HD64F36034FZ@QFP64 [CX3011]  
HD64F36034GH@QFP64 [CX3014]  
HD64F36037FZ@QFP64 [CX3011]  
HD64F36037GH@QFP64 [CX3014]  
HD64F36049GH@QFP80 [CX3018]  
HD64F36054FZ@QFP64 [CX3011]  
HD64F36054GH@QFP64 [CX3014]  
HD64F36057FZ@QFP64 [CX3011]  
HD64F36057GH@QFP64 [CX3014]  
HD64F36064FP@QFP64 [CX3011]  
HD64F36064GH@QFP64 [CX3014]  
HD64F36074GFZ@QFP64 [CX3011]  
HD64F36074GH@QFP64 [CX3014]  
HD64F36074GHW@QFP64 [CX3014]  
HD64F36074GHZW@QFP64 [CX3014]  
HD64F36074LFZW@QFP64 [CX3011]  
HD64F36074LHV@QFP64 [CX3014]  
HD64F36074LHZ@QFP64 [CX3014]  
HD64F36077GFZ@QFP64 [CX3011]  
HD64F36077GH@QFP64 [CX3014]  
HD64F36077GHW@QFP64 [CX3014]  
HD64F36077GHZW@QFP64 [CX3014]  
HD64F36077LFZW@QFP64 [CX3011]  
HD64F36077LHV@QFP64 [CX3014]  
HD64F36077LHZ@QFP64 [CX3014]  
HD64F36078GFZ@QFP64 [CX3011]  
HD64F36078GH@QFP64 [CX3014]  
HD64F36078GHW@QFP64 [CX3014]  
HD64F36078GHZW@QFP64 [CX3014]  
HD64F36078LFZW@QFP64 [CX3011]  
HD64F36078LHV@QFP64 [CX3014]  
HD64F36078LHZ@QFP64 [CX3014]  
HD64F36079GFZ@QFP64 [CX3011]  
HD64F36079GH@QFP64 [CX3014]  
HD64F36079GHW@QFP64 [CX3014]  
HD64F36079GHZW@QFP64 [CX3014]  
HD64F36079LFZW@QFP64 [CX3011]  
HD64F36079LHV@QFP64 [CX3014]  
HD64F36079LHZ@QFP64 [CX3014]  
HD64F36087FP@QFP64 [CX3011]  
HD64F36109F@PQFP100 [CX3022]  
HD64F36109GH@LQFP100 [CX3043]  
HD64F3642AH@TQFP64 [CX3014]  
HD64F3642AW@TQFP80 [CX3016]  
HD64F3643P@SDIP64 [CX0064]  
HD64F3644H@TQFP64 [CX3014]  
HD64F3644W@TQFP80 [CX3016]  
HD64F3664FP@QFP64 [CX3011]  
HD64F3664FY@QFP48 [CX3007]

HD64F36014GFT@QFN48 [CX4021]  
HD64F36014GFY@QFP48 [CX3007]  
HD64F36022FT@QFN48 [CX4021]  
HD64F36022FY@QFP48 [CX3007]  
HD64F36022GFT@QFN48 [CX4021]  
HD64F36022GFY@QFP48 [CX3007]  
HD64F36024FT@QFN48 [CX4021]  
HD64F36024FY@QFP48 [CX3007]  
HD64F36024GFT@QFN48 [CX4021]  
HD64F36024GFY@QFP48 [CX3007]  
HD64F36034GFZ@QFP64 [CX3011]  
HD64F36034H@QFP64 [CX3014]  
HD64F36037GFZ@QFP64 [CX3011]  
HD64F36037H@QFP64 [CX3014]  
HD64F36049H@QFP80 [CX3018]  
HD64F36054GFZ@QFP64 [CX3011]  
HD64F36054H@QFP64 [CX3014]  
HD64F36057GFZ@QFP64 [CX3011]  
HD64F36057H@QFP64 [CX3014]  
HD64F36064GFP@QFP64 [CX3011]  
HD64F36064H@QFP64 [CX3014]  
HD64F36074GFZW@QFP64 [CX3011]  
HD64F36074GHV@QFP64 [CX3014]  
HD64F36074GHZ@QFP64 [CX3014]  
HD64F36074LFZ@QFP64 [CX3011]  
HD64F36074LH@QFP64 [CX3014]  
HD64F36074LHW@QFP64 [CX3014]  
HD64F36074LHZW@QFP64 [CX3014]  
HD64F36077GFZW@QFP64 [CX3011]  
HD64F36077GHV@QFP64 [CX3014]  
HD64F36077GHZ@QFP64 [CX3014]  
HD64F36077LFZ@QFP64 [CX3011]  
HD64F36077LH@QFP64 [CX3014]  
HD64F36077LHW@QFP64 [CX3014]  
HD64F36077LHZW@QFP64 [CX3014]  
HD64F36078GFZW@QFP64 [CX3011]  
HD64F36078GHV@QFP64 [CX3014]  
HD64F36078GHZ@QFP64 [CX3014]  
HD64F36078LFZ@QFP64 [CX3011]  
HD64F36078LH@QFP64 [CX3014]  
HD64F36078LHW@QFP64 [CX3014]  
HD64F36078LHZW@QFP64 [CX3014]  
HD64F36079GFZW@QFP64 [CX3011]  
HD64F36079GHV@QFP64 [CX3014]  
HD64F36079GHZ@QFP64 [CX3014]  
HD64F36079LFZ@QFP64 [CX3011]  
HD64F36079LH@QFP64 [CX3014]  
HD64F36079LHW@QFP64 [CX3014]  
HD64F36079LHZW@QFP64 [CX3014]  
HD64F36087H@QFP64 [CX3014]  
HD64F36109GF@PQFP100 [CX3022]  
HD64F36109H@LQFP100 [CX3043]  
HD64F3642AP@SDIP64 [CX0064]  
HD64F3643H@TQFP64 [CX3014]  
HD64F3643W@TQFP80 [CX3016]  
HD64F3644P@SDIP64 [CX0064]  
HD64F3664BP@SDIP42 [CX0042]  
HD64F3664FX@QFP48 [CX3008]  
HD64F3664GBP@SDIP42 [CX0042]

HD64F3664GFP@QFP64 [CX3011]  
HD64F3664GFY@QFP48 [CX3007]  
HD64F3664H@QFP64 [CX3014]  
HD64F3684GFP@QFP64 [CX3011]  
HD64F3684H@QFP64 [CX3014]  
HD64F3687GFP@QFP64 [CX3011]  
HD64F3687H@QFP64 [CX3014]  
HD64F3694FX@QFP48 [CX3008]  
HD64F3694GFP@QFP64 [CX3011]  
HD64F3694GFY@QFP48 [CX3007]  
HD64F3694H@QFP64 [CX3014]  
HD64F38002H@TQFP64 [CX3014]  
HD64F38004H@TQFP64 [CX3014]  
HD64F38024H@QFP80 [CX3018]  
HD64F38024RH@QFP80 [CX3018]  
HD64F38024W@QFP80 [CX3016]  
HD64F38102H@TQFP64 [CX3014]  
HD64F38104H@TQFP64 [CX3014]  
HD64F38124H@QFP80 [CX3018]  
HD64F38124WI@QFP80 [CX3016]  
HD64F38324HW@QFP80 [CX3018]  
HD64F38324WW@QFP80 [CX3016]  
HD64F38327HW@QFP80 [CX3018]  
HD64F38327WW@QFP80 [CX3016]  
HD64F38424HW@QFP80 [CX3018]  
HD64F38424WW@QFP80 [CX3016]  
HD64F38427HW@QFP80 [CX3018]  
HD64F38427WW@QFP80 [CX3016]  
HD64F39012FT@QFN48 [CX4021]  
HD64F39012FY@QFP48 [CX3007]  
HD64F39012GFT@QFN48 [CX4021]  
HD64F39012GFY@QFP48 [CX3007]  
HD64F39014FT@QFN48 [CX4021]  
HD64F39014FY@QFP48 [CX3007]  
HD64F39014GFT@QFN48 [CX4021]  
HD64F39014GFY@QFP48 [CX3007]  
HD64F39022FT@QFN48 [CX4021]  
HD64F39022FY@QFP48 [CX3007]  
HD64F39022GFT@QFN48 [CX4021]  
HD64F39022GFY@QFP48 [CX3007]  
HD64F39024FT@QFN48 [CX4021]  
HD64F39024FY@QFP48 [CX3007]  
HD64F39024GFT@QFN48 [CX4021]  
HD64F39024GFY@QFP48 [CX3007]  
HD64F7047F50@QFP100 [CX3021]  
HD64F7058F80@PQFP256(\*) [CX3070]  
R4F20102DFB [CX3014-1]  
R4F20102NFB [CX3014-1]  
R4F20102RDFB [CX3014-1]  
R4F20102RNFB [CX3014-1]  
R4F20103DFB [CX3014-1]  
R4F20103NFB [CX3014-1]  
R4F20103RDFB [CX3014-1]  
R4F20103RNFB [CX3014-1]  
R4F20114DFB [CX3014-1]  
R4F20114NFB [CX3014-1]  
R4F20114RDFB [CX3014-1]  
R4F20114RNFB [CX3014-1]  
R4F20115DFB [CX3014-1]

HD64F3664GFX@QFP48 [CX3008]  
HD64F3664GH@QFP64 [CX3014]  
HD64F3684FP@QFP64 [CX3011]  
HD64F3684GH@QFP64 [CX3014]  
HD64F3687FP@QFP64 [CX3011]  
HD64F3687GH@QFP64 [CX3014]  
HD64F3694FP@QFP64 [CX3011]  
HD64F3694FY@QFP48 [CX3007]  
HD64F3694GFX@QFP48 [CX3008]  
HD64F3694GH@QFP64 [CX3014]  
HD64F38002FP@TQFP64 [CX3011]  
HD64F38004FP@TQFP64 [CX3011]  
HD64F38024F@QFP80 [CX3019]  
HD64F38024RF@QFP80 [CX3019]  
HD64F38024RW@QFP80 [CX3016]  
HD64F38102FP@TQFP64 [CX3011]  
HD64F38104FP@TQFP64 [CX3011]  
HD64F38124D@QFP80 [CX3018]  
HD64F38124W@QFP80 [CX3016]  
HD64F38324H@QFP80 [CX3018]  
HD64F38324W@QFP80 [CX3016]  
HD64F38327H@QFP80 [CX3018]  
HD64F38327W@QFP80 [CX3016]  
HD64F38424H@QFP80 [CX3018]  
HD64F38424W@QFP80 [CX3016]  
HD64F38427H@QFP80 [CX3018]  
HD64F38427W@QFP80 [CX3016]  
HD64F39012FP@QFP64 [CX3011]  
HD64F39012FX@QFP48 [CX3008]  
HD64F39012GFP@QFP64 [CX3011]  
HD64F39012GFX@QFP48 [CX3008]  
HD64F39014FP@QFP64 [CX3011]  
HD64F39014FX@QFP48 [CX3008]  
HD64F39014GFP@QFP64 [CX3011]  
HD64F39014GFX@QFP48 [CX3008]  
HD64F39022FP@QFP64 [CX3011]  
HD64F39022FX@QFP48 [CX3008]  
HD64F39022GFP@QFP64 [CX3011]  
HD64F39022GFX@QFP48 [CX3008]  
HD64F39024FP@QFP64 [CX3011]  
HD64F39024FX@QFP48 [CX3008]  
HD64F39024GFP@QFP64 [CX3011]  
HD64F39024GFX@QFP48 [CX3008]  
HD64F7046F50@QFP80 [CX3018]  
HD64F7055F40@PQFP256(\*) [CX3070]  
R4F20102DFA [CX3011-3]  
R4F20102NFA [CX3011-3]  
R4F20102RDFFA [CX3011-3]  
R4F20102RNFA [CX3011-3]  
R4F20103DFA [CX3011-3]  
R4F20103NFA [CX3011-3]  
R4F20103RDFFA [CX3011-3]  
R4F20103RNFA [CX3011-3]  
R4F20114DFA [CX3011-3]  
R4F20114NFA [CX3011-3]  
R4F20114RDFFA [CX3011-3]  
R4F20114RNFA [CX3011-3]  
R4F20115DFA [CX3011-3]  
R4F20115NFA [CX3011-3]

R4F20115NFB [CX3014-1]  
R4F20115RDFB [CX3014-1]  
R4F20115RNFB [CX3014-1]  
R4F20202DFD [CX3018-1]  
R4F20202NFD [CX3018-1]  
R4F20202RDFD [CX3018-1]  
R4F20202RNFD [CX3018-1]  
R4F20203DFD [CX3018-1]  
R4F20203NFD [CX3018-1]  
R4F20203RDFD [CX3018-1]  
R4F20203RNFD [CX3018-1]  
R4F20214DFD [CX3018-1]  
R4F20214NFD [CX3018-1]  
R4F20214RDFD [CX3018-1]  
R4F20214RNFD [CX3018-1]  
R4F20215DFD [CX3018-1]  
R4F20215NFD [CX3018-1]  
R4F20215RDFD [CX3018-1]  
R4F20215RNFD [CX3018-1]  
R4F20222DFD [CX3018-1]  
R4F20222NFD [CX3018-1]  
R4F20222RDFD [CX3018-1]  
R4F20222RNFD [CX3018-1]  
R4F20223DFD [CX3018-1]  
R4F20223NFD [CX3018-1]  
R4F20223RDFD [CX3018-1]  
R4F20223RNFD [CX3018-1]  
R4F20234DFD [CX3018-1]  
R4F20234NFD [CX3018-1]  
R4F20234RDFD [CX3018-1]  
R4F20234RNFD [CX3018-1]  
R4F20235DFD [CX3018-1]  
R4F20235NFD [CX3018-1]  
R4F20235RDFD [CX3018-1]  
R4F20235RNFD [CX3018-1]  
R4F20322RNFE [CX3021-2]  
R4F20323RNFE [CX3021-2]  
R4F20334RNFE [CX3021-2]  
R4F20335RNFE [CX3021-2]  
R5F71242FPV@QFP48(serial) [CX3008]  
R5F71243FPV@QFP48(serial) [CX3008]  
R5F71252FAV@QFP64(serial) [CX3014]  
R5F71252FPV@QFP64(serial) [CX3011]  
R5F71253FAV@QFP64(serial) [CX3014]  
R5F71253FPV@QFP64(serial) [CX3011]  
R5F71374AD80FPV [CX3043]  
R5F71424AK64FPV [CX3043]  
R5F71426AK64FPV [CX3043]  
R5F71426BJ80FPV [CX3043]  
R5F71464FPV@QFP80(serial) [CX3017]  
R5F71474AK64FPV [CX3043]  
R5F71474BJ80FPV [CX3043]  
R5F71475BD80FPV [CX3043]  
R5F71476AK64FPV [CX3043]  
R5F71476BJ80FPV [CX3043]  
R4F20115RDFA [CX3011-3]  
R4F20115RNFA [CX3011-3]  
R4F20202DFC [CX3016-1]  
R4F20202NFC [CX3016-1]  
R4F20202RDFC [CX3016-1]  
R4F20202RNFC [CX3016-1]  
R4F20203DFC [CX3016-1]  
R4F20203NFC [CX3016-1]  
R4F20203RDFC [CX3016-1]  
R4F20203RNFC [CX3016-1]  
R4F20214DFC [CX3016-1]  
R4F20214NFC [CX3016-1]  
R4F20214RDFC [CX3016-1]  
R4F20214RNFC [CX3016-1]  
R4F20215DFC [CX3016-1]  
R4F20215NFC [CX3016-1]  
R4F20215RDFC [CX3016-1]  
R4F20215RNFC [CX3016-1]  
R4F20222DFC [CX3016-1]  
R4F20222NFC [CX3016-1]  
R4F20222RDFC [CX3016-1]  
R4F20222RNFC [CX3016-1]  
R4F20223DFC [CX3016-1]  
R4F20223NFC [CX3016-1]  
R4F20223RDFC [CX3016-1]  
R4F20223RNFC [CX3016-1]  
R4F20234DFC [CX3016-1]  
R4F20234NFC [CX3016-1]  
R4F20234RDFC [CX3016-1]  
R4F20234RNFC [CX3016-1]  
R4F20235DFC [CX3016-1]  
R4F20235NFC [CX3016-1]  
R4F20235RDFC [CX3016-1]  
R4F20235RNFC [CX3016-1]  
R4F20322RDFE [CX3021-2]  
R4F20323RDFE [CX3021-2]  
R4F20334RDFE [CX3021-2]  
R4F20335RDFE [CX3021-2]  
R5F71374AN80FPV [CX3043]  
R5F71424BJ80FPV [CX3043]  
R5F71426BD80FPV [CX3043]  
R5F71464FPV@QFP80 [CX3017]  
R5F71474BD80FPV [CX3043]  
R5F71475AK64FPV [CX3043]  
R5F71475BJ80FPV [CX3043]  
R5F71476BD80FPV [CX3043]

## MICROCONTROLLER

ATT7025@QFP64 [CX3011]

## HOLTEK

### E (E) PROM/FRAM/NVRAM

HT24C01 [CX0001] HT24C01@SOIC8 [CX1045]  
HT24C02 [CX0001] HT24C02@SOIC8 [CX1045]  
HT24C04 [CX0001] HT24C04@SOIC8 [CX1045]  
HT24C08 [CX0001] HT24C16 [CX0001]  
HT24LC01 [CX0001] HT24LC01@SOIC8 [CX1045]  
HT24LC01@TSSOP8 [CX1059] HT24LC02 [CX0001]  
HT24LC02@SOIC8 [CX1045] HT24LC02@TSSOP8 [CX1059]  
HT24LC04 [CX0001] HT24LC04@SOIC8 [CX1045]  
HT24LC08 [CX0001] HT24LC08@SOIC8 [CX1045]  
HT24LC16 [CX0001] HT24LC16@SOIC8 [CX1045]  
HT24LC32 [CX0001] HT24LC32@SOIC8 [CX1045]  
HT24LC64 [CX0001] HT24LC64@SOIC8 [CX1045]  
HT25LC512@SOIC8 [CX1045] HT27C010 [CX0001]  
HT27C010@PLCC32 [CX2032] HT27C010@SOP32 [CX1034]  
HT27C020 [CX0001] HT27C020@PLCC32 [CX2032]  
HT27C020@SOP32 [CX1034] HT27C040 [CX0001]  
HT27C040@PLCC32 [CX2032] HT27C040@SOP32 [CX1034]  
HT27C4096 [CX0001] HT27C4096@PLCC44 [CX2044]  
HT27C512 [CX0001] HT27C512@SOP28 [CX1033]  
HT27C512-A@PLCC32 [CX2032] HT27C512-B@PLCC32 [CX2032]  
HT27LC010 [CX0001] HT27LC010@PLCC32 [CX2032]  
HT27LC010@SOP32 [CX1034] HT27LC010@TSOP32 [CX1002]  
HT27LC020 [CX0001] HT27LC020@PLCC32 [CX2032]  
HT27LC020@SOP32 [CX1034] HT27LC020@TSOP32 [CX1002]  
HT27LC040 [CX0001] HT27LC040@PLCC32 [CX2032]  
HT27LC040@SOP32 [CX1034] HT27LC040@TSOP32 [CX1002]  
HT27LC4096 [CX0001] HT27LC4096@PLCC44 [CX2044]  
HT27LC512 [CX0001] HT27LC512@SOP28 [CX1033]  
HT27LC512@TSOP28 [CX1024] HT27LC512-A@PLCC32 [CX2032]  
HT27LC512-B@PLCC32 [CX2032] HT93C46(16bit) [CX0001]  
HT93C46(16bit)@SOP8-A [CX1045] HT93C46(16bit)@SOP8-B [CX1045]  
HT93C46(16bit)@TSSOP8 [CX1059] HT93C56(16bit) [CX0001]  
HT93C56(16bit)@SOP8-A [CX1045] HT93C56(16bit)@SOP8-B [CX1045]  
HT93C56(16bit)@TSSOP8 [CX1059] HT93C66(16bit) [CX0001]  
HT93C66(16bit)@SOP8-A [CX1045] HT93C66(16bit)@SOP8-B [CX1045]  
HT93C66(16bit)@TSSOP8 [CX1059] HT93LC46A(08bit) [CX0001]  
HT93LC46A(08bit)@SOP8-A [CX1045] HT93LC46A(08bit)@SOP8-B [CX1045]  
HT93LC46A(08bit)@TSSOP8 [CX1059] HT93LC46A(16bit) [CX0001]  
HT93LC46A(16bit)@SOP8-A [CX1045] HT93LC46A(16bit)@SOP8-B [CX1045]  
HT93LC46A(16bit)@TSSOP8 [CX1059] HT93LC46B(08bit) [CX0001]  
HT93LC46B(08bit)@SOP8-A [CX1045] HT93LC46B(08bit)@SOP8-B [CX1045]  
HT93LC46B(08bit)@TSSOP8 [CX1059] HT93LC46B(16bit) [CX0001]  
HT93LC46B(16bit)@SOP8-A [CX1045] HT93LC46B(16bit)@SOP8-B [CX1045]  
HT93LC46B(16bit)@TSSOP8 [CX1059] HT93LC56A(08bit) [CX0001]  
HT93LC56A(08bit)@SOP8-A [CX1045] HT93LC56A(08bit)@SOP8-B [CX1045]  
HT93LC56A(08bit)@TSSOP8 [CX1059] HT93LC56A(16bit) [CX0001]  
HT93LC56A(16bit)@SOP8-A [CX1045] HT93LC56A(16bit)@SOP8-B [CX1045]  
HT93LC56A(16bit)@TSSOP8 [CX1059] HT93LC56B(08bit) [CX0001]  
HT93LC56B(08bit)@SOP8-A [CX1045] HT93LC56B(08bit)@SOP8-B [CX1045]  
HT93LC56B(08bit)@TSSOP8 [CX1059] HT93LC56B(16bit) [CX0001]

HT93LC56B(16bit)@SOP8-A [CX1045]	HT93LC56B(16bit)@SOP8-B [CX1045]
HT93LC56B(16bit)@TSSOP8 [CX1059]	HT93LC66A(08bit) [CX0001]
HT93LC66A(08bit)@SOP8-A [CX1045]	HT93LC66A(08bit)@SOP8-B [CX1045]
HT93LC66A(08bit)@TSSOP8 [CX1059]	HT93LC66A(16bit) [CX0001]
HT93LC66A(16bit)@SOP8-A [CX1045]	HT93LC66A(16bit)@SOP8-B [CX1045]
HT93LC66A(16bit)@TSSOP8 [CX1059]	HT93LC66B(08bit) [CX0001]
HT93LC66B(08bit)@SOP8-A [CX1045]	HT93LC66B(08bit)@SOP8-B [CX1045]
HT93LC66B(08bit)@TSSOP8 [CX1059]	HT93LC66B(16bit) [CX0001]
HT93LC66B(16bit)@SOP8-A [CX1045]	HT93LC66B(16bit)@SOP8-B [CX1045]
HT93LC66B(16bit)@TSSOP8 [CX1059]	HT93LC76(08bit) [CX0001]
HT93LC76(08bit)@SOP8-A [CX1045]	HT93LC76(08bit)@SOP8-B [CX1045]
HT93LC76(08bit)@TSSOP8 [CX1059]	HT93LC76(16bit) [CX0001]
HT93LC76(16bit)@SOP8-A [CX1045]	HT93LC76(16bit)@SOP8-B [CX1045]
HT93LC76(16bit)@TSSOP8 [CX1059]	HT93LC86(08bit) [CX0001]
HT93LC86(08bit)@SOP8-A [CX1045]	HT93LC86(08bit)@SOP8-B [CX1045]
HT93LC86(08bit)@TSSOP8 [CX1059]	HT93LC86(16bit) [CX0001]
HT93LC86(16bit)@SOP8-A [CX1045]	HT93LC86(16bit)@SOP8-B [CX1045]
HT93LC86(16bit)@TSSOP8 [CX1059]	

## MICROCONTROLLER

HT45R38@QFP52 [CX3048]	HT46R22 [CX0001]
HT46R22@SOP24 [CX1033]	HT46R23(dip24) [CX0001]
HT46R23(dip28) [CX0001]	HT46R23@SOP24 [CX1033]
HT46R23@SOP28 [CX1033]	HT46R232 [CX0001]
HT46R232@SOP28 [CX1033]	HT46R232@SSOP48 [CX1028]
HT46R24 [CX0001]	HT46R24@SOP28 [CX1033]
HT46R24@SSOP48 [CX1028]	HT46R342@QFP44 [CX3002]
HT46R46(dip18) [CX0001]	HT46R46(dip20) [CX0001]
HT46R46@SOP18 [CX1033]	HT46R46@SOP20 [CX1033]
HT46R46@SSOP20 [CX1025]	HT46R46-H [CX0001]
HT46R46-H@SOP18 [CX1033]	HT46R47(dip18) [CX0001]
HT46R47(dip20) [CX0001]	HT46R47@SOP18 [CX1033]
HT46R47@SOP20 [CX1033]	HT46R47@SSOP20 [CX1025]
HT46R47-H [CX0001]	HT46R47-H@SOP18 [CX1033]
HT46R48(dip20) [CX0001]	HT46R48(dip24) [CX0001]
HT46R48@SOP20 [CX1033]	HT46R48@SOP24 [CX1033]
HT46R48@SSOP24 [CX1025]	HT46R51A(dip18) [CX0001]
HT46R51A@SOP20 [CX1033]	HT46R51A@SSOP20 [CX1025]
HT46R52A(dip18) [CX0001]	HT46R52A@SOP20 [CX1033]
HT46R52A@SSOP20 [CX1025]	HT46R53A(dip28) [CX0001]
HT46R53A@SOP28 [CX1033]	HT46R54A(dip28) [CX0001]
HT46R54A@SOP28 [CX1033]	HT46R62@SSOP56 [CX1054]
HT46R63@PQFP100 [CX3023]	HT46R63@SSOP56 [CX1054]
HT46R64@PQFP100 [CX3023]	HT46R64@SSOP56 [CX1054]
HT46R65@PQFP100 [CX3023]	HT46R65@SSOP56 [CX1054]
HT46R652@PQFP100 [CX3023]	HT46R71D@SSOP48 [CX1028]
HT46R74D@SSOP56 [CX1054]	HT46RB50 [CX0001]
HT46RB50@SOP28 [CX1033]	HT46RB50@SSOP48 [CX1028]
HT46RB70 [CX0001]	HT46RB70@SOP28 [CX1033]
HT46RB70@SSOP48 [CX1028]	HT46RU22 [CX0001]
HT46RU22@SOP24 [CX1033]	HT46RU22@SSOP24 [CX1025]
HT46RU25@SSOP48 [CX1028]	HT46RU25@SSOP56 [CX1054]
HT47R10A@QFP44 [CX3002]	HT47R20A@QFP64 [CX3049]
HT48R05A [CX0001]	HT48R05A@SOP16 [CX1000]
HT48R05A@SOP18 [CX1033]	HT48R06A [CX0001]
HT48R06A@SOP16 [CX1016]	HT48R06A@SOP18 [CX1033]
HT48R07A [CX0001]	HT48R07A@SOP24 [CX1033]
HT48R07A@SSOP24 [CX1025]	HT48R08A [CX0001]



HT48R08A@SOP16 [CX1000]  
HT48R09A [CX0001]  
HT48R09A@SSOP24 [CX1025]  
HT48R10A@SOP24 [CX1033]  
HT48R30A(dip28) [CX0001]  
HT48R30A@SOP28 [CX1033]  
HT48R502A@SSOP48 [CX1028]  
HT48R50A@SOP28 [CX1028]  
HT48R52A@QFP44 [CX3002]  
HT48R54A@QFP52 [CX3048]  
HT48R70A@SSOP48 [CX1028]  
HT48RA0-1@SOP24 [CX1033]  
HT48RA0-2@SOP20 [CX1033]  
HT48RA0-3 [CX0001]  
HT48RA1@SOP28 [CX1033]  
HT48RA3 [CX0001]  
HT48RA3@SSOP28 [CX1025]  
HT48RA5@SOP28 [CX1033]  
HT48RB50 [CX0001]  
HT48RB50@SSOP48 [CX1028]  
HT48RB8@SSOP48 [CX1028]  
HT49R30A@SSOP48 [CX1028]  
HT49R50A@SSOP48 [CX1028]  
HT49RU80@QFP100 [CX3023]  
HT49RV5@SSOP56 [CX1054]  
HT82A523R@LQFP32 [CX3001]  
HT82A523R@LQFP64 [CX30UN]  
HT82A821R@SOP24 [CX1033]  
HT82A822R@SSOP48 [CX1028]  
HT82A832R@SSOP48 [CX1028]  
HT82J97E@SOP28 [CX1033]  
HT82K68E@SOP20 [CX1033]  
HT82K68E@SSOP48 [CX1028]  
HT82K95A@QFN32 [CX4015]  
HT82K95A@SSOP48 [CX1028]  
HT82K95E@SOP20 [CX1033]  
HT82K95E@SSOP48 [CX1028]  
HT82K96A@SSOP48 [CX1028]  
HT82K96E(dip40) [CX0001]  
HT82K96E@SOP28 [CX1033]  
HT82M99E(dip18) [CX0001]  
HT82M99E@SOP18 [CX1033]  
HT82M9AE@SOP20 [CX1033]  
HT82M9AE@SSOP20 [CX1025]  
HT82M9BE@SOP24 [CX1033]  
HT82M9BE@SSOP24 [CX1025]  
HT95A100@SOP28 [CX1033]  
HT95A200@SSOP48 [CX1028]  
HT95A300@SSOP48 [CX1028]  
HT95A400@PQFP64  
HT95L000@SSOP56 [CX1054]  
HT95L100@PQFP64 [CX3049]  
HT95L200@QFP100 [CX3023]  
HT95L300@QFP100 [CX3023]  
HT48R08A@SOP18 [CX1033]  
HT48R09A@SOP24 [CX1033]  
HT48R10A [CX0001]  
HT48R30A(dip24) [CX0001]  
HT48R30A@SOP24 [CX1033]  
HT48R502A@QFP64  
HT48R50A [CX0001]  
HT48R50A@SSOP48 [CX1028]  
HT48R54A@QFP44 [CX3002]  
HT48R70A@PQFP64 [CX3049]  
HT48RA0-1 [CX0001]  
HT48RA0-2 [CX0001]  
HT48RA0-2@SSOP20 [CX1025]  
HT48RA0-3@SOP20 [CX1033]  
HT48RA1@SSOP28 [CX1026]  
HT48RA3@SOP28 [CX1033]  
HT48RA5 [CX0001]  
HT48RA5@SSOP28 [CX1025]  
HT48RB50@SOP28 [CX1033]  
HT48RB8@SOP28 [CX1033]  
HT49R10A@QFP44 [CX3002]  
HT49R50A@QFP100 [CX3023]  
HT49R70A@QFP100 [CX3023]  
HT49RV3@QFP52 [CX3048]  
HT49RV7@PQFP100 [CX3023]  
HT82A523R@LQFP52 [CX3048]  
HT82A523R@SSOP48 [CX1028]  
HT82A821R@SSOP24 [CX1025]  
HT82A832R@QFP48 [CX3007]  
HT82J97E@SOP20 [CX1033]  
HT82K68E [CX0001]  
HT82K68E@SOP28 [CX1033]  
HT82K94E@SSOP48 [CX1028]  
HT82K95A@SOP28 [CX1033]  
HT82K95E@QFN32 [CX4015]  
HT82K95E@SOP28 [CX1033]  
HT82K96A@SOP28 [CX1033]  
HT82K96E(dip20) [CX0001]  
HT82K96E@SOP20 [CX1033]  
HT82K96E@SSOP48 [CX1028]  
HT82M99E(dip20) [CX0001]  
HT82M99E@SOP20 [CX1033]  
HT82M9AE@SOP24 [CX1033]  
HT82M9AE@SSOP24 [CX1025]  
HT82M9BE@SOP28 [CX1033]  
HT82M9BE@SSOP28 [CX1026]  
HT95A10P@SOP28 [CX1033]  
HT95A20P@SSOP48 [CX1028]  
HT95A30P@SSOP48 [CX1028]  
HT95A40P@PQFP64  
HT95L00P@SSOP56 [CX1054]  
HT95L10P@PQFP64 [CX3049]  
HT95L20P@QFP100 [CX3023]  
HT95L30P@QFP100 [CX3023]

## HONEYWELL

E (E) PROM/FRAM/NVRAM

HXNV0100@QFP64 [CX3011]

## HONGKONG

### E (E) PROM/FRAM/NVRAM

HK1215 [CX0001]	HK1225 [CX0001]
HK1235 [CX0001]	HK1245
HK1255	HK1265
HK1275 [CX0001]	HK1285 [CX0001]
HK1295 [CX0001]	HK12A5 [CX0001]
HK12B5 [CX0001]	OKS1225 [CX0001]
OKS1235 [CX0001]	OKS1245
OKS1255	OKS1265
OKS1275 [CX0001]	OKS1285 [CX0001]
OKS1295 [CX0001]	OKS12A5 [CX0001]
OKS12B5 [CX0001]	

## HOPEFIND

### E (E) PROM/FRAM/NVRAM

HM24LC01 [CX0001]	HM24LC01@SOP8 [CX1045]
HM24LC01@TSSOP8 [CX1059]	HM24LC02 [CX0001]
HM24LC02@SOP8 [CX1045]	HM24LC02@TSSOP8 [CX1059]
HM24LC04 [CX0001]	HM24LC04@SOP8 [CX1045]
HM24LC04@TSSOP8 [CX1059]	HM24LC08 [CX0001]
HM24LC08@SOP8 [CX1045]	HM24LC08@TSSOP8 [CX1059]
HM24LC16 [CX0001]	HM24LC16@SOP8 [CX1045]
HM24LC16@TSSOP8 [CX1059]	

## HUAJIE Technology

### E (E) PROM/FRAM/NVRAM

K24C02 [CX0001]	K24C02@SOP8 [CX1045]
K24C02@TSSOP8 [CX1059]	K24C02C [CX0001]
K24C02C@SOP8 [CX1045]	K24C02C@TSSOP8 [CX1059]
K24C04 [CX0001]	K24C04@SOP8 [CX1045]
K24C04@TSSOP8 [CX1059]	K24C04C [CX0001]
K24C04C@SOP8 [CX1045]	K24C04C@TSSOP8 [CX1059]
K24C08 [CX0001]	K24C08@SOP8 [CX1045]
K24C08@TSSOP8 [CX1059]	K24C08C [CX0001]
K24C08C@SOP8 [CX1045]	K24C08C@TSSOP8 [CX1059]
K24C16 [CX0001]	K24C16@SOP8 [CX1045]
K24C16@TSSOP8 [CX1059]	K24C16C [CX0001]
K24C16C@SOP8 [CX1045]	K24C16C@TSSOP8 [CX1059]
K34C02 [CX0001]	K34C02@SOP8 [CX1045]
K34C02@TSSOP8 [CX1059]	

## HUAWEI

### MICROCONTROLLER

AT89C51ED2@PLCC44 [CX2044]  
SD5000RQ1@LQFP176 [CX3058]

SD5000@LQFP176 [CX3058]

## HYNITRON

### MICROCONTROLLER

CSM212 [CX1033-8]  
CSM212-S [CX1016-4]  
CSM216-Q [CX4011-1]  
CSM224 [CX1033-8]  
CSM224-S [CX1026-1]

CSM212-Q [CX4008]  
CSM216 [CX1033-8]  
CSM216-S [CX1026-1]  
CSM224-Q [CX4033-1]

## HYNIX

### E (E) PROM/FRAM/NVRAM

H27S1G8F2BFR@FBGA63 [CX5046]  
H27U1G8F2BTR@TSOP48 [CX1004-3]  
H27U2G8F2CTR@TSOP48 [CX1004-3]  
H27U4G8T2BTR@TSOP48 [CX1004-3]  
H27U518S2CTR@TSOP48 [CX1004]  
H27U8G8T2B@TSOP48 [CX1004-1]  
H27UAG8T2BTR@TSOP48 [CX1004-3]  
H27UBG8T2ATR@TSOP48 [CX1004-3]  
HY2764 [CX0001]  
HY27SF081G2A@FBGA63 [CX5046]  
HY27UF081G2A@FBGA63 [CX5046]  
HY27UF081G2M@TSOP48 [CX1004]  
HY27UF082G2B@TSOP48 [CX1004-1]  
HY27UF084G2B@TSOP48 [CX1004-3]  
HY27UG088G5B@TSOP48 [CX1004]  
HY27US08121A@FBGA63 [CX5046]  
HY27US08121B@TSOP48 [CX1004]  
HY27US081G1M@USOP48 [CX1042]  
HY27US08561A@TSOP48 [CX1004]  
HY27US08561M@TSOP48 [CX1004]  
HY27UT084G2M@TSOP48 [CX1004]  
HY27UT088G2M@TSOP48 [CX1004]  
HY27UV08BG5M@TSOP48 [CX1004]  
HY29DL162BT@TSOP48 [CX1004]  
HY29DL162TT@TSOP48 [CX1004]  
HY29DL163BT@TSOP48 [CX1004]  
HY29DL163TT@TSOP48 [CX1004]  
HY29DS162BT@TSOP48 [CX1004]  
HY29DS162TT@TSOP48 [CX1004]  
HY29DS163BT@TSOP48 [CX1004]  
HY29DS163TT@TSOP48 [CX1004]  
HY29F002T@PLCC32 [CX2032]  
HY29F040 [CX0001]  
HY29F040@TSOP32 [CX1002]  
HY29F040A@PLCC32 [CX2032]  
HY29F080@TSOP40 [CX1006]  
HY29F200B@TSOP48 [CX1004]  
HY29F200T@TSOP48 [CX1004]  
HY29F400ABT@TSOP48 [CX1004]  
HY29F400ATT@TSOP48 [CX1004]

H27U1G8F2BFR@FBGA63 [CX5046]  
H27U1G8F2CTR@TSOP48 [CX1004-1]  
H27U4G8F2DTR@TSOP48 [CX1004-3]  
H27U518S2CTP@TSOP48 [CX1004]  
H27U8G8G5DTR@TSOP48 [CX1004-1]  
H27UAG8T2ATR@TSOP48 [CX1004]  
H27UAG8T2MTR@TSOP48 [CX1004-1]  
H27UBG8U5MTR@TSOP48 [CX1004-1]  
HY27C64A [CX0001]  
HY27UA081G1M@TSOP48 [CX1004]  
HY27UF081G2A@TSOP48 [CX1004-3]  
HY27UF082G2A@TSOP48 [CX1004]  
HY27UF082G2M@TSOP48 [CX1004]  
HY27UF084G2M@TSOP48 [CX1004]  
HY27UG088G5M@TSOP48 [CX1004]  
HY27US08121A@TSOP48 [CX1004]  
HY27US08121M@TSOP48 [CX1004]  
HY27US08281A@TSOP48 [CX1004]  
HY27US08561A@WSOP48 [CX1042]  
HY27UT084G2A@TSOP48 [CX1004]  
HY27UT088G2A@TSOP48 [CX1004]  
HY27UU088G5M@TSOP48 [CX1004-1]  
HY29DL162BF@FBGA48 [CX5022]  
HY29DL162TF@FBGA48 [CX5022]  
HY29DL163BF@FBGA48 [CX5022]  
HY29DL163TF@FBGA48 [CX5022]  
HY29DS162BF@FBGA48 [CX5022]  
HY29DS162TF@FBGA48 [CX5022]  
HY29DS163BF@FBGA48 [CX5022]  
HY29DS163TF@FBGA48 [CX5022]  
HY29F002T [CX0001]  
HY29F002T@TSOP32 [CX1002]  
HY29F040@PLCC32 [CX2032]  
HY29F040A [CX0001]  
HY29F040A@TSOP32 [CX1002]  
HY29F200B@PSOP44 [CX1014]  
HY29F200T@PSOP44 [CX1014]  
HY29F400ABG@PSOP44 [CX1014]  
HY29F400ATG@PSOP44 [CX1014]  
HY29F400BG@PSOP44 [CX1014]

HY29F400BT@TSOP48 [CX1004]  
HY29F400TT@TSOP48 [CX1004]  
HY29F800ABT@TSOP48 [CX1004]  
HY29F800ATT@TSOP48 [CX1004]  
HY29F800BT@TSOP48 [CX1004]  
HY29F800TT@TSOP48 [CX1004]  
HY29LV160BT@TSOP48 [CX1004]  
HY29LV160TT@TSOP48 [CX1004]  
HY29LV320BF@FBGA63 [CX5047]  
HY29LV320TF@FBGA48 [CX50UN]  
HY29LV320TT@TSOP48 [CX1004]  
HY29LV400BT@TSOP48 [CX1004]  
HY29LV400TT@TSOP48 [CX1004]  
HY29LV800BG@PSOP44 [CX1014]  
HY29LV800TF@FBGA48 [CX5002]  
HY29LV800TT@TSOP48 [CX1004]  
HY93C46@SOIC8 [CX1045]  
HY93C56@SOIC8 [CX1045]  
HY93C66@SOIC8 [CX1045]  
HY93C76@SOIC8 [CX1045]  
HY93C86@SOIC8 [CX1045]

HY29F400TG@PSOP44 [CX1014]  
HY29F800ABG@PSOP44 [CX1014]  
HY29F800ATG@PSOP44 [CX1014]  
HY29F800BG@PSOP44 [CX1014]  
HY29F800TG@PSOP44 [CX1014]  
HY29LV160BF@FBGA48 [CX5022]  
HY29LV160TF@FBGA48 [CX5022]  
HY29LV320BF@FBGA48 [CX50UN]  
HY29LV320BT@TSOP48 [CX1004]  
HY29LV320TF@FBGA63 [CX5047]  
HY29LV400BF@FBGA48 [CX5002]  
HY29LV400TF@FBGA48 [CX5002]  
HY29LV800BF@FBGA48 [CX5002]  
HY29LV800BT@TSOP48 [CX1004]  
HY29LV800TG@PSOP44 [CX1014]  
HY93C46 [CX0001]  
HY93C56 [CX0001]  
HY93C66 [CX0001]  
HY93C76 [CX0001]  
HY93C86 [CX0001]

#### DRAM & SRAM

HY62256A [CX0001]  
HY6264A [CX0001]

HY62256A@TSOP28 [CX1001]  
HY6264A@TSOP28 [CX1001]

#### MICROCONTROLLER

GMS34004TK [CX0001]  
GMS34004TW [CX0001]  
GMS34112TK@SOIC20 [CX1033]  
GMS34140TK [CX0001]  
GMS81004(dip20) [CX0001]  
GMS81004(dip28) [CX0001]  
GMS81004@SOIC20 [CX1033]  
GMS81004@SOIC28 [CX1033]  
GMS81008(dip24) [CX0001]  
GMS81008@PLCC44 [CX2044]  
GMS81008@SOIC24 [CX1033]  
GMS81016(dip20) [CX0001]  
GMS81016(dip28) [CX0001]  
GMS81016@SOIC20 [CX1033]  
GMS81016@SOIC28 [CX1033]  
GMS81024(dip24) [CX0001]  
GMS81024@PLCC44 [CX2044]  
GMS81024@SOIC24 [CX1033]  
GMS81032(dip20) [CX0001]  
GMS81032(dip28) [CX0001]  
GMS81032@SOIC20 [CX1033]  
GMS81032@SOIC28 [CX1033]  
GMS81504T [CX0032]  
GMS81516AT [CX0001]  
GMS81524 [CX0001]  
GMS81524BT [CX0001]  
GMS81604T@PLCC44 [CX2044]  
GMS81608T [CX0001]  
GMS81608T@SDIP42 [CX0042]

GMS34004TM [CX0001]  
GMS34112TK [CX0001]  
GMS34112TK@SSOP20 [CX1026]  
GMS34140TK@SOIC24 [CX1033]  
GMS81004(dip24) [CX0001]  
GMS81004@PLCC44 [CX2044]  
GMS81004@SOIC24 [CX1033]  
GMS81008(dip20) [CX0001]  
GMS81008(dip28) [CX0001]  
GMS81008@SOIC20 [CX1033]  
GMS81008@SOIC28 [CX1033]  
GMS81016(dip24) [CX0001]  
GMS81016@PLCC44 [CX2044]  
GMS81016@SOIC24 [CX1033]  
GMS81024(dip20) [CX0001]  
GMS81024(dip28) [CX0001]  
GMS81024@SOIC20 [CX1033]  
GMS81024@SOIC28 [CX1033]  
GMS81032(dip24) [CX0001]  
GMS81032@PLCC44 [CX2044]  
GMS81032@SOIC24 [CX1033]  
GMS81504AT [CX0032]  
GMS81516 [CX0001]  
GMS81516BT [CX0001]  
GMS81524AT [CX0001]  
GMS81604T [CX0001]  
GMS81604T@SDIP42 [CX0042]  
GMS81608T@PLCC44 [CX2044]  
GMS81C5016(dip28) [CX0001]

GMS81C5016(dip40) [CX0001]                   GMS81C5016@PLCC44 [CX2044]  
GMS81C5016@SOIC28 [CX1033]                   GMS81C5016@TQFP44 [CX3002]  
GMS81C5024(dip28) [CX0001]                   GMS81C5024(dip40) [CX0001]  
GMS81C5024@PLCC44 [CX2044]                   GMS81C5024@SOIC28 [CX1033]  
GMS81C5024@TQFP44 [CX3002]                   GMS81C5032(dip28) [CX0001]  
GMS81C5032(dip40) [CX0001]                   GMS81C5032@PLCC44 [CX2044]  
GMS81C5032@SOIC28 [CX1033]                   GMS81C5032@TQFP44 [CX3002]  
GMS82516T [CX0001]                            GMS82516T@MQFP44 [CX3002]  
GMS82516T@SDIP42 [CX0042]                   GMS82524T [CX0001]  
GMS82524T@MQFP44 [CX3002]                   GMS82524T@SDIP42 [CX0042]  
GMS87C1102 [CX0001]                           GMS87C1102@SOP16 [CX1033]  
GMS87C1202 [CX0001]                           GMS87C1202@SOP20 [CX1033]  
GMS87C1404 [CX0001]                           GMS87C1404@SOP28 [CX1033]  
GMS87C1408 [CX0001]                           GMS87C1408@SOP28 [CX1033]  
GMS87C5032(dip28) [CX0001]                   GMS87C5032(dip40) [CX0001]  
GMS87C5032@PLCC44 [CX2044]                   GMS87C5032@SOIC28 [CX1033]  
GMS87C5032@TQFP44 [CX3002]                   GMS97C1051 [CX0001]  
GMS97C1051@SOIC20 [CX1033]                   GMS97C2051 [CX0001]  
GMS97C2051@SOIC20 [CX1033]                   GMS97C51 [CX0001]  
GMS97C51@PLCC44 [CX2044]                    GMS97C51@TQFP44 [CX3002]  
GMS97C52 [CX0001]                            GMS97C52@PLCC44 [CX2044]  
GMS97C52@TQFP44 [CX3002]                    GMS97C54 [CX0001]  
GMS97C54@PLCC44 [CX2044]                    GMS97C54@TQFP44 [CX3002]  
GMS97C56 [CX0001]                            GMS97C56@PLCC44 [CX2044]  
GMS97C56@TQFP44 [CX3002]                    GMS97C58 [CX0001]  
GMS97C58@PLCC44 [CX2044]                    GMS97C58@TQFP44 [CX3002]  
GMS97L1051 [CX0001]                           GMS97L1051@SOIC20 [CX1033]  
GMS97L2051 [CX0001]                           GMS97L2051@SOIC20 [CX1033]  
GMS97L51 [CX0001]                            GMS97L51@PLCC44 [CX2044]  
GMS97L51@TQFP44 [CX3002]                    GMS97L52 [CX0001]  
GMS97L52@PLCC44 [CX2044]                    GMS97L52@TQFP44 [CX3002]  
GMS97L54 [CX0001]                            GMS97L54@PLCC44 [CX2044]  
GMS97L54@TQFP44 [CX3002]                    GMS97L56 [CX0001]  
GMS97L56@PLCC44 [CX2044]                    GMS97L56@TQFP44 [CX3002]  
GMS97L58 [CX0001]                            GMS97L58@PLCC44 [CX2044]  
GMS97L58@TQFP44 [CX3002]                    GMS99C51 [CX0001]  
GMS99C51@PLCC44 [CX2044]                    GMS99C51@TQFP44 [CX3002]  
GMS99C52 [CX0001]                            GMS99C52@PLCC44 [CX2044]  
GMS99C52@TQFP44 [CX3002]                    GMS99C58 [CX0001]  
GMS99C58@PLCC44 [CX2044]                    GMS99C58@TQFP44 [CX3002]  
HMS81004E(dip20) [CX0001]                   HMS81004E(dip24) [CX0001]  
HMS81004E(dip28) [CX0001]                   HMS81004E@PLCC44 [CX2044]  
HMS81004E@SOIC20 [CX1033]                   HMS81004E@SOIC24 [CX1033]  
HMS81004E@SOIC28 [CX1033]                   HMS81008E(dip20) [CX0001]  
HMS81008E(dip24) [CX0001]                   HMS81008E(dip28) [CX0001]  
HMS81008E@PLCC44 [CX2044]                   HMS81008E@SOIC20 [CX1033]  
HMS81008E@SOIC24 [CX1033]                   HMS81008E@SOIC28 [CX1033]  
HMS81016E(dip20) [CX0001]                   HMS81016E(dip24) [CX0001]  
HMS81016E(dip28) [CX0001]                   HMS81016E@PLCC44 [CX2044]  
HMS81016E@SOIC20 [CX1033]                   HMS81016E@SOIC24 [CX1033]  
HMS81016E@SOIC28 [CX1033]                   HMS81020ET(dip20) [CX0001]  
HMS81020ET(dip24) [CX0001]                   HMS81020ET(dip28) [CX0001]  
HMS81020ET@SOIC20 [CX1033]                   HMS81020ET@SOIC24 [CX1033]  
HMS81020ET@SOIC28 [CX1033]                   HMS81020TL(dip20) [CX0001]  
HMS81020TL(dip24) [CX0001]                   HMS81020TL(dip28) [CX0001]  
HMS81020TL@SOIC20 [CX1033]                   HMS81020TL@SOIC24 [CX1033]  
HMS81020TL@SOIC28 [CX1033]                   HMS81024E(dip20) [CX0001]  
HMS81024E(dip24) [CX0001]                   HMS81024E(dip28) [CX0001]  
HMS81024E@PLCC44 [CX2044]                   HMS81024E@SOIC20 [CX1033]

HMS81024E@SOIC24 [CX1033]  
HMS81032(dip20) [CX0001]  
HMS81032(dip28) [CX0001]  
HMS81032@SOIC24 [CX1033]  
HMS81032ET(dip20) [CX0001]  
HMS81032ET(dip28) [CX0001]  
HMS81032ET@SOIC24 [CX1033]  
HMS81032T(dip20) [CX0001]  
HMS81032T(dip28) [CX0001]  
HMS81032T@SOIC24 [CX1033]  
HMS81032TL(dip20) [CX0001]  
HMS81032TL(dip28) [CX0001]  
HMS81032TL@SOIC24 [CX1033]  
HMS87C1102A [CX0001]  
HMS87C1104A [CX0001]  
HMS87C1202A [CX0001]  
HMS87C1204A [CX0001]  
HMS87C1302A@SDIP24 [CX0032]  
HMS87C1304A@SDIP24 [CX0032]  
HMS87C1404B [CX0001]  
HMS87C1404B@SOIC28 [CX1033]  
HMS87C1408B@SDIP28 [CX0032]  
HMS87C1416B [CX0001]  
HMS87C1416B@SOIC28 [CX1033]  
HMS87C1516B [CX0001]  
HMS87C1616B [CX0001]  
HMS87C1716B@SDIP42 [CX0042]  
HMS87C1816B@TQFP44 [CX3002]  
HMS87C5216@PLCC44 [CX2044]  
HMS87C5216@TQFP44 [CX3002]  
HMS99C51@PLCC44 [CX2044]  
HMS99C52 [CX0001]  
HMS99C52@TQFP44 [CX3002]  
HMS99C58@PLCC44 [CX2044]

HMS81024E@SOIC28 [CX1033]  
HMS81032(dip24) [CX0001]  
HMS81032@SOIC20 [CX1033]  
HMS81032@SOIC28 [CX1033]  
HMS81032ET(dip24) [CX0001]  
HMS81032ET@SOIC20 [CX1033]  
HMS81032ET@SOIC28 [CX1033]  
HMS81032T(dip24) [CX0001]  
HMS81032T@SOIC20 [CX1033]  
HMS81032T@SOIC28 [CX1033]  
HMS81032TL(dip24) [CX0001]  
HMS81032TL@SOIC20 [CX1033]  
HMS81032TL@SOIC28 [CX1033]  
HMS87C1102A@SOP16 [CX1033]  
HMS87C1104A@SOP16 [CX1033]  
HMS87C1202A@SOP20 [CX1033]  
HMS87C1204A@SOP20 [CX1033]  
HMS87C1302A@SOP24 [CX1033]  
HMS87C1304A@SOP24 [CX1033]  
HMS87C1404B@SDIP28 [CX0032]  
HMS87C1408B [CX0001]  
HMS87C1408B@SOIC28 [CX1033]  
HMS87C1416B@SDIP28 [CX0032]  
HMS87C1508B [CX0001]  
HMS87C1608B [CX0001]  
HMS87C1708B@SDIP42 [CX0042]  
HMS87C1808B@TQFP44 [CX3002]  
HMS87C5216 [CX0001]  
HMS87C5216@SOIC28 [CX1033]  
HMS99C51 [CX0001]  
HMS99C51@TQFP44 [CX3002]  
HMS99C52@PLCC44 [CX2044]  
HMS99C58 [CX0001]  
HMS99C58@TQFP44 [CX3002]

## HYNIX(HYUNDAI)

### PLD

HY18CV8J@PLCC20 [CX2020]  
HY18CV8S@SOIC20 [CX1033]

HY18CV8P [CX0001]  
HY18CV8T@TSOP20 [CX1000]

## HYNIX-CUSTOMER

### E (E) PROM/FRAM/NVRAM

H27U1G8F2BFR@FBGA63 (MOTOROLA) [CX5046]  
H27U1G8F2BTR@TSOP48 (MOTOROLA) [CX1004-1]

## HYUNDAI

### E (E) PROM/FRAM/NVRAM

HY2764 [CX0001]  
HY29DL162BF@FBGA48 [CX5022]  
HY29DL162TF@FBGA48 [CX5022]

HY27C64A [CX0001]  
HY29DL162BT@TSOP48 [CX1004]  
HY29DL162TT@TSOP48 [CX1004]

HY29DL163BF@FBGA48 [CX5022]	HY29DL163BT@TSOP48 [CX1004]
HY29DL163TF@FBGA48 [CX5022]	HY29DL163TT@TSOP48 [CX1004]
HY29DS162BF@FBGA48 [CX5022]	HY29DS162BT@TSOP48 [CX1004]
HY29DS162TF@FBGA48 [CX5022]	HY29DS162TT@TSOP48 [CX1004]
HY29DS163BF@FBGA48 [CX5022]	HY29DS163BT@TSOP48 [CX1004]
HY29DS163TF@FBGA48 [CX5022]	HY29DS163TT@TSOP48 [CX1004]
HY29F002T [CX0001]	HY29F002T@PLCC32 [CX2032]
HY29F002T@TSOP32 [CX1002]	HY29F040 [CX0001]
HY29F040@PLCC32 [CX2032]	HY29F040@TSOP32 [CX1002]
HY29F040A [CX0001]	HY29F040A@PLCC32 [CX2032]
HY29F040A@TSOP32 [CX1002]	HY29F080@TSOP40 [CX1006]
HY29F200B@PSOP44 [CX1014]	HY29F200B@TSOP48 [CX1004]
HY29F200T@PSOP44 [CX1014]	HY29F200T@TSOP48 [CX1004]
HY29F400ABG@PSOP44 [CX1014]	HY29F400ABT@TSOP48 [CX1004]
HY29F400ATG@PSOP44 [CX1014]	HY29F400ATT@TSOP48 [CX1004]
HY29F400BG@PSOP44 [CX1014]	HY29F400BT@TSOP48 [CX1004]
HY29F400TG@PSOP44 [CX1014]	HY29F400TT@TSOP48 [CX1004]
HY29F800ABG@PSOP44 [CX1014]	HY29F800ABT@TSOP48 [CX1004]
HY29F800ATG@PSOP44 [CX1014]	HY29F800ATT@TSOP48 [CX1004]
HY29F800BG@PSOP44 [CX1014]	HY29F800BT@TSOP48 [CX1004]
HY29F800TG@PSOP44 [CX1014]	HY29F800TT@TSOP48 [CX1004]
HY29LV160BF@FBGA48 [CX5022]	HY29LV160BT@TSOP48 [CX1004]
HY29LV160TF@FBGA48 [CX5022]	HY29LV160TT@TSOP48 [CX1004]
HY29LV320BF@FBGA48 [CX50UN]	HY29LV320BF@FBGA63 [CX5047]
HY29LV320BT@TSOP48 [CX1004]	HY29LV320TF@FBGA48 [CX50UN]
HY29LV320TF@FBGA63 [CX5047]	HY29LV320TT@TSOP48 [CX1004]
HY29LV400BF@FBGA48 [CX5002]	HY29LV400BT@TSOP48 [CX1004]
HY29LV400TF@FBGA48 [CX5002]	HY29LV400TT@TSOP48 [CX1004]
HY29LV800BF@FBGA48 [CX5002]	HY29LV800BG@PSOP44 [CX1014]
HY29LV800BT@TSOP48 [CX1004]	HY29LV800TF@FBGA48 [CX5002]
HY29LV800TG@PSOP44 [CX1014]	HY29LV800TT@TSOP48 [CX1004]
HY93C46 [CX0001]	HY93C46@SOIC8 [CX1045]
HY93C56 [CX0001]	HY93C56@SOIC8 [CX1045]
HY93C66 [CX0001]	HY93C66@SOIC8 [CX1045]
HY93C76 [CX0001]	HY93C76@SOIC8 [CX1045]
HY93C86 [CX0001]	HY93C86@SOIC8 [CX1045]

#### DRAM & SRAM

HY62256A [CX0001]	HY62256A@TSOP28 [CX1001]
HY6264A [CX0001]	HY6264A@TSOP28 [CX1001]

#### MICROCONTROLLER

GMS34004TK [CX0001]	GMS34004TM [CX0001]
GMS34004TW [CX0001]	GMS34112TK [CX0001]
GMS34112TK@SOIC20 [CX1033]	GMS34112TK@SSOP20 [CX1026]
GMS34140TK [CX0001]	GMS34140TK@SOIC24 [CX1033]
GMS81004(dip20) [CX0001]	GMS81004(dip24) [CX0001]
GMS81004(dip28) [CX0001]	GMS81004@PLCC44 [CX2044]
GMS81004@SOIC20 [CX1033]	GMS81004@SOIC24 [CX1033]
GMS81004@SOIC28 [CX1033]	GMS81008(dip20) [CX0001]
GMS81008(dip24) [CX0001]	GMS81008(dip28) [CX0001]
GMS81008@PLCC44 [CX2044]	GMS81008@SOIC20 [CX1033]
GMS81008@SOIC24 [CX1033]	GMS81008@SOIC28 [CX1033]
GMS81016(dip20) [CX0001]	GMS81016(dip24) [CX0001]
GMS81016(dip28) [CX0001]	GMS81016@PLCC44 [CX2044]
GMS81016@SOIC20 [CX1033]	GMS81016@SOIC24 [CX1033]

GMS81016@SOIC28 [CX1033]  
GMS81024(dip24) [CX0001]  
GMS81024@PLCC44 [CX2044]  
GMS81024@SOIC24 [CX1033]  
GMS81032(dip20) [CX0001]  
GMS81032(dip28) [CX0001]  
GMS81032@SOIC20 [CX1033]  
GMS81032@SOIC28 [CX1033]  
GMS81504T [CX0032]  
GMS81516AT [CX0001]  
GMS81524 [CX0001]  
GMS81524BT [CX0001]  
GMS81604T@PLCC44 [CX2044]  
GMS81608T [CX0001]  
GMS81608T@SDIP42 [CX0042]  
GMS81C5016(dip40) [CX0001]  
GMS81C5016@SOIC28 [CX1033]  
GMS81C5024(dip28) [CX0001]  
GMS81C5024@PLCC44 [CX2044]  
GMS81C5024@TQFP44 [CX3002]  
GMS81C5032(dip40) [CX0001]  
GMS81C5032@SOIC28 [CX1033]  
GMS82516T [CX0001]  
GMS82516T@SDIP42 [CX0042]  
GMS82524T@MQFP44 [CX3002]  
GMS87C1102 [CX0001]  
GMS87C1202 [CX0001]  
GMS87C1404 [CX0001]  
GMS87C1408 [CX0001]  
GMS87C5032(dip28) [CX0001]  
GMS87C5032@PLCC44 [CX2044]  
GMS87C5032@TQFP44 [CX3002]  
GMS97C1051@SOIC20 [CX1033]  
GMS97C2051@SOIC20 [CX1033]  
GMS97C51@PLCC44 [CX2044]  
GMS97C52 [CX0001]  
GMS97C52@TQFP44 [CX3002]  
GMS97C54@PLCC44 [CX2044]  
GMS97C56 [CX0001]  
GMS97C56@TQFP44 [CX3002]  
GMS97C58@PLCC44 [CX2044]  
GMS97L1051 [CX0001]  
GMS97L2051 [CX0001]  
GMS97L51 [CX0001]  
GMS97L51@TQFP44 [CX3002]  
GMS97L52@PLCC44 [CX2044]  
GMS97L54 [CX0001]  
GMS97L54@TQFP44 [CX3002]  
GMS97L56@PLCC44 [CX2044]  
GMS97L58 [CX0001]  
GMS97L58@TQFP44 [CX3002]  
GMS99C51@PLCC44 [CX2044]  
GMS99C52 [CX0001]  
GMS99C52@TQFP44 [CX3002]  
GMS99C58@PLCC44 [CX2044]  
HMS81004E(dip20) [CX0001]  
HMS81004E(dip28) [CX0001]  
HMS81004E@SOIC20 [CX1033]  
HMS81004E@SOIC28 [CX1033]  
GMS81024(dip20) [CX0001]  
GMS81024(dip28) [CX0001]  
GMS81024@SOIC20 [CX1033]  
GMS81024@SOIC28 [CX1033]  
GMS81032(dip24) [CX0001]  
GMS81032@PLCC44 [CX2044]  
GMS81032@SOIC24 [CX1033]  
GMS81504AT [CX0032]  
GMS81516 [CX0001]  
GMS81516BT [CX0001]  
GMS81524AT [CX0001]  
GMS81604T [CX0001]  
GMS81604T@SDIP42 [CX0042]  
GMS81608T@PLCC44 [CX2044]  
GMS81C5016(dip28) [CX0001]  
GMS81C5016@PLCC44 [CX2044]  
GMS81C5016@TQFP44 [CX3002]  
GMS81C5024(dip40) [CX0001]  
GMS81C5024@SOIC28 [CX1033]  
GMS81C5032(dip28) [CX0001]  
GMS81C5032@PLCC44 [CX2044]  
GMS81C5032@TQFP44 [CX3002]  
GMS82516T@MQFP44 [CX3002]  
GMS82524T [CX0001]  
GMS82524T@SDIP42 [CX0042]  
GMS87C1102@SOP16 [CX1033]  
GMS87C1202@SOP20 [CX1033]  
GMS87C1404@SOP28 [CX1033]  
GMS87C1408@SOP28 [CX1033]  
GMS87C5032(dip40) [CX0001]  
GMS87C5032@SOIC28 [CX1033]  
GMS97C1051 [CX0001]  
GMS97C2051 [CX0001]  
GMS97C51 [CX0001]  
GMS97C51@TQFP44 [CX3002]  
GMS97C52@PLCC44 [CX2044]  
GMS97C54 [CX0001]  
GMS97C54@TQFP44 [CX3002]  
GMS97C56@PLCC44 [CX2044]  
GMS97C58 [CX0001]  
GMS97C58@TQFP44 [CX3002]  
GMS97L1051@SOIC20 [CX1033]  
GMS97L2051@SOIC20 [CX1033]  
GMS97L51@PLCC44 [CX2044]  
GMS97L52 [CX0001]  
GMS97L52@TQFP44 [CX3002]  
GMS97L54@PLCC44 [CX2044]  
GMS97L56 [CX0001]  
GMS97L56@TQFP44 [CX3002]  
GMS97L58@PLCC44 [CX2044]  
GMS99C51 [CX0001]  
GMS99C51@TQFP44 [CX3002]  
GMS99C52@PLCC44 [CX2044]  
GMS99C58 [CX0001]  
GMS99C58@TQFP44 [CX3002]  
HMS81004E(dip24) [CX0001]  
HMS81004E@PLCC44 [CX2044]  
HMS81004E@SOIC24 [CX1033]  
HMS81008E(dip20) [CX0001]



HMS81008E(dip24) [CX0001]	HMS81008E(dip28) [CX0001]
HMS81008E@PLCC44 [CX2044]	HMS81008E@SOIC20 [CX1033]
HMS81008E@SOIC24 [CX1033]	HMS81008E@SOIC28 [CX1033]
HMS81016E(dip20) [CX0001]	HMS81016E(dip24) [CX0001]
HMS81016E(dip28) [CX0001]	HMS81016E@PLCC44 [CX2044]
HMS81016E@SOIC20 [CX1033]	HMS81016E@SOIC24 [CX1033]
HMS81016E@SOIC28 [CX1033]	HMS81020ET(dip20) [CX0001]
HMS81020ET(dip24) [CX0001]	HMS81020ET(dip28) [CX0001]
HMS81020ET@SOIC20 [CX1033]	HMS81020ET@SOIC24 [CX1033]
HMS81020ET@SOIC28 [CX1033]	HMS81020TL(dip20) [CX0001]
HMS81020TL(dip24) [CX0001]	HMS81020TL(dip28) [CX0001]
HMS81020TL@SOIC20 [CX1033]	HMS81020TL@SOIC24 [CX1033]
HMS81020TL@SOIC28 [CX1033]	HMS81024E(dip20) [CX0001]
HMS81024E(dip24) [CX0001]	HMS81024E(dip28) [CX0001]
HMS81024E@PLCC44 [CX2044]	HMS81024E@SOIC20 [CX1033]
HMS81024E@SOIC24 [CX1033]	HMS81024E@SOIC28 [CX1033]
HMS81032(dip20) [CX0001]	HMS81032(dip24) [CX0001]
HMS81032(dip28) [CX0001]	HMS81032@SOIC20 [CX1033]
HMS81032@SOIC24 [CX1033]	HMS81032@SOIC28 [CX1033]
HMS81032ET(dip20) [CX0001]	HMS81032ET(dip24) [CX0001]
HMS81032ET(dip28) [CX0001]	HMS81032ET@SOIC20 [CX1033]
HMS81032ET@SOIC24 [CX1033]	HMS81032ET@SOIC28 [CX1033]
HMS81032T(dip20) [CX0001]	HMS81032T(dip24) [CX0001]
HMS81032T(dip28) [CX0001]	HMS81032T@SOIC20 [CX1033]
HMS81032T@SOIC24 [CX1033]	HMS81032T@SOIC28 [CX1033]
HMS81032TL(dip20) [CX0001]	HMS81032TL(dip24) [CX0001]
HMS81032TL(dip28) [CX0001]	HMS81032TL@SOIC20 [CX1033]
HMS81032TL@SOIC24 [CX1033]	HMS81032TL@SOIC28 [CX1033]
HMS87C1102A [CX0001]	HMS87C1102A@SOP16 [CX1033]
HMS87C1104A [CX0001]	HMS87C1104A@SOP16 [CX1033]
HMS87C1202A [CX0001]	HMS87C1202A@SOP20 [CX1033]
HMS87C1204A [CX0001]	HMS87C1204A@SOP20 [CX1033]
HMS87C1302A@SDIP24 [CX0032]	HMS87C1302A@SOP24 [CX1033]
HMS87C1304A@SDIP24 [CX0032]	HMS87C1304A@SOP24 [CX1033]
HMS87C1404B [CX0001]	HMS87C1404B@SDIP28 [CX0032]
HMS87C1404B@SOIC28 [CX1033]	HMS87C1408B [CX0001]
HMS87C1408B@SDIP28 [CX0032]	HMS87C1408B@SOIC28 [CX1033]
HMS87C1416B [CX0001]	HMS87C1416B@SDIP28 [CX0032]
HMS87C1416B@SOIC28 [CX1033]	HMS87C1508B [CX0001]
HMS87C1516B [CX0001]	HMS87C1608B [CX0001]
HMS87C1616B [CX0001]	HMS87C1708B@SDIP42 [CX0042]
HMS87C1716B@SDIP42 [CX0042]	HMS87C1808B@TQFP44 [CX3002]
HMS87C1816B@TQFP44 [CX3002]	HMS87C5216 [CX0001]
HMS87C5216@PLCC44 [CX2044]	HMS87C5216@SOIC28 [CX1033]
HMS87C5216@TQFP44 [CX3002]	HMS99C51 [CX0001]
HMS99C51@PLCC44 [CX2044]	HMS99C51@TQFP44 [CX3002]
HMS99C52 [CX0001]	HMS99C52@PLCC44 [CX2044]
HMS99C52@TQFP44 [CX3002]	HMS99C58 [CX0001]
HMS99C58@PLCC44 [CX2044]	HMS99C58@TQFP44 [CX3002]

## IC Microsystems

### E (E) PROM/FRAM/NVRAM

X24C00 [CX0001]	X24C00@MSOP8 [CX1015]
X24C00@SOIC8 [CX1045]	X24C01 [CX0001]
X24C01@MSOP8 [CX1015]	X24C01@SOIC14 [CX1030]
X24C01@SOIC8 [CX1045]	X24C01A [CX0001]

X24C01A@MSOP8 [CX1015]  
X24C02 [CX0001]  
X24C02@SOIC14 [CX1030]  
X24C04 [CX0001]  
X24C04@SOIC14 [CX1030]  
X24C08 [CX0001]  
X24C08@SOIC14 [CX1030]  
X24C16 [CX0001]  
X24C16@SOIC14 [CX1030]

X24C01A@SOIC8 [CX1045]  
X24C02@MSOP8 [CX1015]  
X24C02@SOIC8 [CX1045]  
X24C04@MSOP8 [CX1015]  
X24C04@SOIC8 [CX1045]  
X24C08@MSOP8 [CX1015]  
X24C08@SOIC8 [CX1045]  
X24C16@MSOP8 [CX1015]  
X24C16@SOIC8 [CX1045]

## ICE

### E (E) PROM/FRAM/NVRAM

ICE25P05 [CX0001]  
ICE27C010 [CX0001]  
ICE27C010@TSOP32 [CX1002]  
ICE27C020@PLCC32 [CX2032]  
ICE27C512 [CX0001]  
ICE27C512@TSOP28 [CX1024]  
ICE27LC010@PLCC32 [CX2032]  
ICE27LC020 [CX0001]  
ICE27LC020@TSOP32 [CX1002]  
ICE27LC512@PLCC32 [CX2032]  
ICE28LF010 [CX0001]  
ICE37C512 [CX0001]  
ICE37C512@TSOP32 [CX1002]  
ICE37LC512@PLCC32 [CX2032]

ICE25P05@SOIC8 [CX1045]  
ICE27C010@PLCC32 [CX2032]  
ICE27C020 [CX0001]  
ICE27C020@TSOP32 [CX1002]  
ICE27C512@PLCC32 [CX2032]  
ICE27LC010 [CX0001]  
ICE27LC010@TSOP32 [CX1002]  
ICE27LC020@PLCC32 [CX2032]  
ICE27LC512 [CX0001]  
ICE27LC512@TSOP28 [CX1024]  
ICE28LF010@PLCC32 [CX2032]  
ICE37C512@PLCC32 [CX2032]  
ICE37LC512 [CX0001]  
ICE37LC512@TSOP32 [CX1002]

## ICMIC

### E (E) PROM/FRAM/NVRAM

X76F101 [CX0001]  
X76F400@SOIC8 [CX1000]

X76F101@SOIC8 [CX1045]  
X76F400@TSSOP8 [CX1000]

## ICSI

### E (E) PROM/FRAM/NVRAM

IC71V08F32AS04@FBGA64 [CX5026]  
IC71V08F32AS08@FBGA64 [CX5026]  
IC71V08F32BS04@FBGA64 [CX5026]  
IC71V08F32BS08@FBGA64 [CX5026]  
IC71V08F32CS04@FBGA64 [CX5026]  
IC71V08F32CS08@FBGA64 [CX5026]  
IC71V08F32DS04@FBGA64 [CX5026]  
IC71V08F32DS08@FBGA64 [CX5026]  
IC71V08F32ES04@FBGA64 [CX5026]  
IC71V08F32ES08@FBGA64 [CX5026]  
IC71V08F32FS04@FBGA64 [CX5026]  
IC71V08F32FS08@FBGA64 [CX5026]  
IC71V16F32AS04@FBGA64 [CX5026]  
IC71V16F32AS08@FBGA64 [CX5026]  
IC71V16F32BS04@FBGA64 [CX5026]  
IC71V16F32BS08@FBGA64 [CX5026]

IC71V08F32AS04@FBGA73 [CX5026]  
IC71V08F32AS08@FBGA73 [CX5026]  
IC71V08F32BS04@FBGA73 [CX5026]  
IC71V08F32BS08@FBGA73 [CX5026]  
IC71V08F32CS04@FBGA73 [CX5026]  
IC71V08F32CS08@FBGA73 [CX5026]  
IC71V08F32DS04@FBGA73 [CX5026]  
IC71V08F32DS08@FBGA73 [CX5026]  
IC71V08F32ES04@FBGA73 [CX5026]  
IC71V08F32ES08@FBGA73 [CX5026]  
IC71V08F32FS04@FBGA73 [CX5026]  
IC71V08F32FS08@FBGA73 [CX5026]  
IC71V16F32AS04@FBGA73 [CX5026]  
IC71V16F32AS08@FBGA73 [CX5026]  
IC71V16F32BS04@FBGA73 [CX5026]  
IC71V16F32BS08@FBGA73 [CX5026]

IC71V16F32CS04@FBGA64 [CX5026]  
IC71V16F32CS08@FBGA64 [CX5026]  
IC71V16F32DS04@FBGA64 [CX5026]  
IC71V16F32DS08@FBGA64 [CX5026]  
IC71V16F32ES04@FBGA64 [CX5026]  
IC71V16F32ES08@FBGA64 [CX5026]  
IC71V16F32FS04@FBGA64 [CX5026]  
IC71V16F32FS08@FBGA64 [CX5026]  
IC71V16F32GS04@FBGA73 [CX5001]  
IC71V16F32HS04@FBGA73 [CX5001]  
IC71V16F64IP16@FBGA73 [CX5001]

IC71V16F32CS04@FBGA73 [CX5026]  
IC71V16F32CS08@FBGA73 [CX5026]  
IC71V16F32DS04@FBGA73 [CX5026]  
IC71V16F32DS08@FBGA73 [CX5026]  
IC71V16F32ES04@FBGA73 [CX5026]  
IC71V16F32ES08@FBGA73 [CX5026]  
IC71V16F32FS04@FBGA73 [CX5026]  
IC71V16F32FS08@FBGA73 [CX5026]  
IC71V16F32GS08@FBGA73 [CX5001]  
IC71V16F32HS08@FBGA73 [CX5001]  
IC71V16F64IS08@FBGA73 [CX5001]

## MICROCONTROLLER

IC89LV51A [CX0001]  
IC89LV51A@TQFP44 [CX3002]  
IC89LV52A@PLCC44 [CX2044]  
IS89C51A [CX0001]  
IS89C51A@TQFP44 [CX3002]  
IS89C52A@PLCC44 [CX2044]  
IS89C54 [CX0001]  
IS89C54@TQFP44 [CX3002]  
IS89C58@PLCC44 [CX2044]  
IS89C64 [CX0001]  
IS89C64@TQFP44 [CX3002]  
IS89E54@PLCC44 [CX2044]  
IS89E58 [CX0001]  
IS89E58@TQFP44 [CX3002]  
IS89E64@PLCC44 [CX2044]

IC89LV51A@PLCC44 [CX2044]  
IC89LV52A [CX0001]  
IC89LV52A@TQFP44 [CX3002]  
IS89C51A@PLCC44 [CX2044]  
IS89C52A [CX0001]  
IS89C52A@TQFP44 [CX3002]  
IS89C54@PLCC44 [CX2044]  
IS89C58 [CX0001]  
IS89C58@TQFP44 [CX3002]  
IS89C64@PLCC44 [CX2044]  
IS89E54 [CX0001]  
IS89E54@TQFP44 [CX3002]  
IS89E58@PLCC44 [CX2044]  
IS89E64 [CX0001]  
IS89E64@TQFP44 [CX3002]

## ICT

### E (E) PROM/FRAM/NVRAM

27CX010 [CX0001]  
27CX010@TSOP32 [CX1002]  
27CX321 [CX0001]  
27CX641 [CX0001]  
93C46 [CX0001]  
93C46A [CX0001]  
93C56A [CX0001]  
93C66A [CX0001]  
93CX46 [CX0001]  
93CX56 [CX0001]  
93CX66 [CX0001]

27CX010@PLCC32 [CX2032]  
27CX256 [CX0001]  
27CX322 [CX0001]  
27CX642 [CX0001]  
93C46@SOIC8 [CX1045]  
93C46A@SOIC8 [CX1045]  
93C56A@SOIC8 [CX1045]  
93C66A@SOIC8 [CX1045]  
93CX46@SOIC8 [CX1045]  
93CX56@SOIC8 [CX1045]  
93CX66@SOIC8 [CX1045]

### PLD

PA7024 [CX0001]  
PA7024(JN)@PLCC28 [CX2028]  
PA7140 [CX0001]  
PA7140@TQFP44 [CX3003]  
PA7540(J)@PLCC28 [CX2028]  
PA7572 [CX0001]  
PA7572@TQFP44 [CX3003]  
PEEL173 [CX0001]  
PEEL18CV8P [CX0001]

PA7024(J)@PLCC28 [CX2028]  
PA7024@SOIC24 [CX1033]  
PA7140@PLCC44 [CX2044]  
PA7540 [CX0001]  
PA7540(JN)@PLCC28 [CX2028]  
PA7572@PLCC44 [CX2044]  
PEEL153 [CX0001]  
PEEL18CV8J@PLCC20 [CX2020]  
PEEL18CV8S@SOIC20 [CX1033]

PEEL18CV8T@TSOP20 [CX1000]  
PEEL18CV8Z@PLCC20 [CX2020]  
PEEL18CV8Z@TSOP20 [CX1000]  
PEEL18LV8Z@PLCC20 [CX2020]  
PEEL18LV8Z@TSOP20 [CX1000]  
PEEL22CV10A@PLCC28 [CX2028]  
PEEL22CV10A@TSOP24 [CX1000]  
PEEL22CV10A+@PLCC28 [CX2028]  
PEEL22CV10A+@TSOP24 [CX1000]  
PEEL22CV10A++@PLCC28 [CX2028]  
PEEL22CV10A++@TSOP24 [CX1000]  
PEEL22CV10AZ@PLCC28 [CX2028]  
PEEL22CV10AZ@TSOP24 [CX1000]  
PEEL22CV10AZ+@PLCC28 [CX2028]  
PEEL22CV10AZ+@TSOP24 [CX1000]  
PEEL22CV10AZ++@PLCC28 [CX2028]  
PEEL22CV10AZ++@TSOP24 [CX1000]  
PEEL22LV10AZ@PLCC28 [CX2028]  
PEEL22LV10AZ@TSOP24 [CX1000]  
PEEL22LV10AZ+@PLCC28 [CX2028]  
PEEL22LV10AZ+@TSOP24 [CX1000]  
PEEL22LV10AZ++@PLCC28 [CX2028]  
PEEL22LV10AZ++@TSOP24 [CX1000]  
PEEL273 [CX0001]

PEEL18CV8Z [CX0001]  
PEEL18CV8Z@SOIC20 [CX1033]  
PEEL18LV8Z [CX0001]  
PEEL18LV8Z@SOIC20 [CX1033]  
PEEL22CV10A [CX0001]  
PEEL22CV10A@SOIC24 [CX1033]  
PEEL22CV10A+ [CX0001]  
PEEL22CV10A+@SOIC24 [CX1033]  
PEEL22CV10A++ [CX0001]  
PEEL22CV10A++@SOIC24 [CX1033]  
PEEL22CV10AZ [CX0001]  
PEEL22CV10AZ@SOIC24 [CX1033]  
PEEL22CV10AZ+ [CX0001]  
PEEL22CV10AZ+@SOIC24 [CX1033]  
PEEL22CV10AZ++ [CX0001]  
PEEL22CV10AZ++@SOIC24 [CX1033]  
PEEL22LV10AZ [CX0001]  
PEEL22LV10AZ@SOIC24 [CX1033]  
PEEL22LV10AZ+ [CX0001]  
PEEL22LV10AZ+@SOIC24 [CX1033]  
PEEL22LV10AZ++ [CX0001]  
PEEL22LV10AZ++@SOIC24 [CX1033]  
PEEL253 [CX0001]

## IDT

### E (E) PROM/FRAM/NVRAM

IDT5V9885@TQFP32 [CX3001]

IDT5V9885@VFQFPN28 [CX4014]

## IK Semiconductor

### E (E) PROM/FRAM/NVRAM

IK24LC02B [CX0001]  
IK24LC04B [CX0001]  
IK24LC08B [CX0001]  
IK24LC16B [CX0001]

IK24LC02B@SOIC8 [CX1045]  
IK24LC04B@SOIC8 [CX1045]  
IK24LC08B@SOIC8 [CX1045]  
IK24LC16B@SOIC8 [CX1045]

## ILITEK

### MICROCONTROLLER

M2VQN000@QFP48 [CX3007-5]

## IML

### E (E) PROM/FRAM/NVRAM

AUO-G1422.2H@TQFN32 [CX4015]

iML1991@QFN32 [CX4015]

## IMT

## E (E) PROM/FRAM/NVRAM

IM29F001B [CX0001]	
IM29F001B(REVERSE)@TSOP32 [CX1002]	
IM29F001B@PLCC32 [CX2032]	IM29F001B@TSOP32 [CX1002]
IM29F001B@VSOP32 [CX1003]	IM29F001T [CX0001]
IM29F001T(REVERSE)@TSOP32 [CX1002]	
IM29F001T@PLCC32 [CX2032]	IM29F001T@TSOP32 [CX1002]
IM29F001T@VSOP32 [CX1003]	IM29F002B [CX0001]
IM29F002B(REVERSE)@TSOP32 [CX1002]	
IM29F002B@PLCC32 [CX2032]	IM29F002B@TSOP32 [CX1002]
IM29F002B@VSOP32 [CX1003]	IM29F002T [CX0001]
IM29F002T(REVERSE)@TSOP32 [CX1002]	
IM29F002T@PLCC32 [CX2032]	IM29F002T@TSOP32 [CX1002]
IM29F002T@VSOP32 [CX1003]	IM29F004B [CX0001]
IM29F004B(REVERSE)@TSOP32 [CX1002]	
IM29F004B@PLCC32 [CX2032]	IM29F004B@TSOP32 [CX1002]
IM29F004B@VSOP32 [CX1003]	IM29F004T [CX0001]
IM29F004T(REVERSE)@TSOP32 [CX1002]	
IM29F004T@PLCC32 [CX2032]	IM29F004T@TSOP32 [CX1002]
IM29F004T@VSOP32 [CX1003]	IM29LV004B [CX0001]
IM29LV004B(REVERSE)@TSOP32 [CX1002]	
IM29LV004B@PLCC32 [CX2032]	IM29LV004B@TSOP32 [CX1002]
IM29LV004B@VSOP32 [CX1003]	IM29LV004T [CX0001]
IM29LV004T(REVERSE)@TSOP32 [CX1002]	
IM29LV004T@PLCC32 [CX2032]	IM29LV004T@TSOP32 [CX1002]
IM29LV004T@VSOP32 [CX1003]	IM29LV400B@PSOP44 [CX1014]
IM29LV400B@TSOP48 [CX1043]	IM29LV400T@PSOP44 [CX1014]
IM29LV400T@TSOP48 [CX1043]	

## INFINEON

### MICROCONTROLLER

PMA7105@TSSOP38 [CX1012]	SAB-C501G-1E [CX0001]
SAB-C501G-1E@PLCC44 [CX2044]	SAB-C501G-1E@TQFP44 [CX3002]
SAB-C504-2EM@TQFP44 [CX3002]	SAB-C505A-4EM@TQFP44 [CX3002]
SAB-C505CA-4EM@TQFP44 [CX3002]	SAB-C505L-4EM@PQFP80 [CX3018]
SAB-C508-4EM@TQFP64 [CX3014]	SAB-C508-4EP@SDIP64 [CX0064]
SAB-C515C-8EM@TQFP80 [CX3018]	SAB-C540U-1EN@PLCC44 [CX2044]
SAB-C540U-1EP@SDIP52 [CX0052]	SAB-C541U-1EN@PLCC44 [CX2044]
SAB-C541U-1EP@SDIP52 [CX0052]	SAF-C501G-1EN@PLCC44 [CX2044]
SAF-C501G-1EP [CX0001]	SAF-C504-2EM@TQFP44 [CX3002]
SAF-C505A-4EM@TQFP44 [CX3002]	SAF-C505CA-4EM@TQFP44 [CX3002]
SAF-C505L-4EM@PQFP80 [CX3018]	SAF-C508-4EM@TQFP64 [CX3014]
SAF-C508-4EP@SDIP64 [CX0064]	SAF-C513AO-2EM@TQFP44 [CX3002]
SAF-C513AO-2EN@PLCC44 [CX2044]	SAF-C513AO-2EP [CX0001]
SAF-C515C-8EM@TQFP80 [CX3018]	SAF-XC822-1FRI@TSSOP16 [CX1000]
SAF-XC822M-1FRI@TSSOP16 [CX1000]	
SAF-XC822MT-1FRI@TSSOP16 [CX1000]	SAF-XC822T-1FRI@TSSOP16 [CX1000]
SAF-XC822T-0FRI@TSSOP16 [CX1000]	SAF-XC824MT-1FGI@SOIC20 [CX1033]
SAF-XC824M-1FGI@SOIC20 [CX1033]	SAF-XC836-2FRI@TSSOP28 [CX1001]
SAF-XC835MT-2FGI@SOIC24 [CX1033]	SAF-XC836M-2FRI@TSSOP28 [CX1001]
SAF-XC836M-1FRI@TSSOP28 [CX1001]	
SAF-XC836MT-2FRA@TSSOP28 [CX1001]	
SAF-XC836MT-2FRI@TSSOP28 [CX1001]	
SAF-XC836T-2FRI@TSSOP28 [CX1001]	
SAF-XC856CLM-13FFI@QFP64 [CX3011]	

SAF-XC856CLM-16FFI@QFP64 [CX3011]  
SAF-XC856CLM-9FFI@QFP64 [CX3011] SAF-XC856LM-13FFI@QFP64 [CX3011]  
SAF-XC856LM-16FFI@QFP64 [CX3011] SAF-XC856LM-9FFI@QFP64 [CX3011]  
SAF-XC858CA-13FFI(5v)@QFP64 [CX3011]  
SAF-XC858CA-16FFI(5v)@QFP64 [CX3011]  
SAF-XC858CA-9FFI(5v)@QFP64 [CX3011]  
SAF-XC878-13FFI(3.3v)@QFP64 [CX3011]  
SAF-XC878-13FFI(5v)@QFP64 [CX3011]  
SAF-XC878-16FFI(3.3v)@QFP64 [CX3011]  
SAF-XC878-16FFI(5v)@QFP64 [CX3011]  
SAF-XC878CM-13FFI(3.3v)@QFP64 [CX3011]  
SAF-XC878CM-13FFI(5v)@QFP64 [CX3011]  
SAF-XC878CM-16FFI(3.3v)@QFP64 [CX3011]  
SAF-XC878CM-16FFI(5v)@QFP64 [CX3011]  
SAF-XC878M-13FFI(3.3v)@QFP64 [CX3011]  
SAF-XC878M-13FFI(5v)@QFP64 [CX3011]  
SAF-XC878M-16FFI(3.3v)@QFP64 [CX3011]  
SAF-XC878M-16FFI(5v)@QFP64 [CX3011]  
SAF-XC886-6FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886-6FFA(5v)@QFP48 [CX3007]  
SAF-XC886-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886-8FFI(5v)@QFP48 [CX3007]  
SAF-XC886C-6FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886C-6FFA(5v)@QFP48 [CX3007]  
SAF-XC886C-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886C-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886C-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886C-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886C-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886C-8FFI(5v)@QFP48 [CX3007]  
SAF-XC886CLM-6FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886CLM-6FFA(5v)@QFP48 [CX3007]  
SAF-XC886CLM-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CLM-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFI(5v)@QFP48 [CX3007]  
SAF-XC886CM-6FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-6FFA(5v)@QFP48 [CX3007]  
SAF-XC886CM-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886CM-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886CM-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-8FFI(5v)@QFP48 [CX3007]  
SAF-XC886LM-6FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-6FFA(5v)@QFP48 [CX3007]  
SAF-XC886LM-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886LM-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886LM-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-8FFI(5v)@QFP48 [CX3007]  
SAF-XC888-6FFA(3.3v)@QFP64 [CX3011]

SAF-XC888-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888C-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888C-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888C-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888C-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888C-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888C-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888C-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888C-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888CM-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888CM-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888CM-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888CM-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888LM-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888LM-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888LM-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888LM-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888LM-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888LM-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888LM-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888LM-8FFI(5v)@QFP64 [CX3011]  
SAH-C504-2EM@TQFP44 [CX3002]                   SAH-C505A-4EM@TQFP44 [CX3002]  
SAH-C505CA-4EM@TQFP44 [CX3002]               SAK-C504-2EM@TQFP44 [CX3002]  
SAK-C505A-4EM@TQFP44 [CX3002]               SAK-C505CA-4EM@TQFP44 [CX3002]  
SAK-C505L-4EM@PQFP80 [CX3018]               SAK-C515C-8EM@TQFP80 [CX3018]  
SAK-XC824M-1FGI@SOIC20 [CX1033]  
SAK-XC886-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886C-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886C-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886C-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886C-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886C-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886C-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886C-8FFI(3.3v)@QFP48 [CX3007]

SAK-XC886C-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886CM-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886CM-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886CM-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886CM-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886LM-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886LM-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886LM-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886LM-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-8FFI(5v)@QFP48 [CX3007]  
SAK-XC888-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888C-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888C-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888C-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888C-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888C-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888C-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888C-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888C-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888CM-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888CM-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888CM-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888CM-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888LM-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-6FFA(5v)@QFP64 [CX3011]



SAK-XC888LM-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888LM-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888LM-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-8FFI(5v)@QFP64 [CX3011]  
SAX-XC824M-1FGI@SOIC20 [CX1033]  
SAX-XC878-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878-16FFA(5v)@QFP64 [CX3011]  
SAX-XC878C-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878C-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878C-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878C-16FFA(5v)@QFP64 [CX3011]  
SAX-XC878CM-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878CM-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878CM-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878CM-16FFA(5v)@QFP64 [CX3011]  
SAX-XC878L-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878L-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878L-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878L-16FFA(5v)@QFP64 [CX3011]  
TLE7810G@SOIC28 [CX1033]

## INTEGRAL

### E (E) PROM/FRAM/NVRAM

IN24AA02A [CX0001]	IN24AA02A@SOIC8 [CX1045]
IN24AA02B [CX0001]	IN24AA02B@SOIC8 [CX1045]
IN24LC02B [CX0001]	IN24LC02B@SOIC8 [CX1045]
IN24LC04B [CX0001]	IN24LC04B@SOIC8 [CX1045]
IN24LC08B [CX0001]	IN24LC08B@SOIC8 [CX1045]
IN24LC16B [CX0001]	IN24LC16B@SOIC8 [CX1045]

## INTEL

### E (E) PROM/FRAM/NVRAM

27010 [CX0001]	27010@PLCC32 [CX2032]
27010@TSOP32 [CX1002]	27128 [CX0001]
27128A [CX0001]	27128B [CX0001]
2716 [CX0001]	27210 [CX0001]
27256 [CX0001]	2732 [CX0001]
2732A [CX0001]	27512 [CX0001]
2764 [CX0001]	2764A [CX0001]
27C010 [CX0001]	27C010@PLCC32 [CX2032]
27C010@TSOP32 [CX1002]	27C010A [CX0001]
27C010A@PLCC32 [CX2032]	27C010A@TSOP32 [CX1002]
27C020 [CX0001]	27C020@PLCC32 [CX2032]
27C020@TSOP32 [CX1002]	27C040 [CX0001]
27C040@PLCC32 [CX2032]	27C040@TSOP32 [CX1002]
27C100 [CX0001]	27C100@PLCC32 [CX2032]
27C100@TSOP32 [CX1002]	27C128 [CX0001]
27C128@PLCC32 [CX2032]	27C210 [CX0001]
27C210@PLCC44 [CX2044]	27C220 [CX0001]

27C220@PLCC44 [CX2044]	27C240 [CX0001]
27C240@PLCC44 [CX2044]	27C256 [CX0001]
27C256@PLCC32 [CX2032]	27C400 [CX0001]
27C400@PLCC44 [CX2044]	27C512 [CX0001]
27C512@PLCC32 [CX2032]	27C64 [CX0001]
27C64@PLCC32 [CX2032]	27C800 [CX0001]
27S512 [CX0001]	2816A [CX0001]
2817A [CX0001]	2864A [CX0001]
68C257 [CX0001]	68C257@PLCC32 [CX2032]
87C256 [CX0001]	87C257 [CX0001]
87C257@PLCC32 [CX2032]	87C64 [CX0001]
D27011 [CX0001]	D27513 [CX0001]
D27C011 [CX0001]	D27C513 [CX0001]
D2816 [CX0001]	D28F256 [CX0001]
D28F256A [CX0001]	D28F512 [CX0001]
DA28F016SA@SSOP56 [CX1029]	DA28F016SV@SSOP56 [CX1029]
DA28F320J5@SSOP56 [CX1029]	DA28F320J5A@SSOP56 [CX1029]
DA28F640J5@SSOP56 [CX1029]	DA28F640J5A@SSOP56 [CX1029]
DD28F032SA@TSOP56 [CX1055]	DT28F016SA@SSOP56 [CX1029]
DT28F016SA@TSOP56 [CX1055]	DT28F016SV@SSOP56 [CX1029]
DT28F016SV@TSOP56 [CX1055]	DT28F160F3B@SSOP56 [CX1029]
DT28F160F3T@SSOP56 [CX1029]	DT28F160S3@SSOP56 [CX1029]
DT28F160S5@SSOP56 [CX1029]	DT28F320J5@SSOP56 [CX1029]
DT28F320J5A@SSOP56 [CX1029]	DT28F320S3@SSOP56 [CX1029]
DT28F320S5@SSOP56 [CX1029]	DT28F640J5@SSOP56 [CX1029]
DT28F640J5A@SSOP56 [CX1029]	DT28F800F3B@SSOP56 [CX1029]
DT28F800F3T@SSOP56 [CX1029]	E28F001BX-B@TSOP32 [CX1002]
E28F001BX-T@TSOP32 [CX1002]	E28F002BCT@TSOP40 [CX1006]
E28F002BEB@TSOP40 [CX1006]	E28F002BET@TSOP40 [CX1006]
E28F002BLB@TSOP40 [CX1006]	E28F002BLT@TSOP40 [CX1006]
E28F002BVB@TSOP40 [CX1006]	E28F002BVT@TSOP40 [CX1006]
E28F002BXB@TSOP40 [CX1006]	E28F002BXT@TSOP40 [CX1006]
E28F004B5B@TSOP40 [CX1006]	E28F004B5T@TSOP40 [CX1006]
E28F004BEB@TSOP40 [CX1006]	E28F004BET@TSOP40 [CX1006]
E28F004BLB@TSOP40 [CX1006]	E28F004BLT@TSOP40 [CX1006]
E28F004BVB@TSOP40 [CX1006]	E28F004BVT@TSOP40 [CX1006]
E28F004BXB@TSOP40 [CX1006]	E28F004BXT@TSOP40 [CX1006]
E28F004S3@TSOP40 [CX1006]	E28F004S5@TSOP40 [CX1006]
E28F004SC@TSOP40 [CX1006]	E28F008BEB@TSOP40 [CX1006]
E28F008BET@TSOP40 [CX1006]	E28F008BLB@TSOP40 [CX1006]
E28F008BLT@TSOP40 [CX1006]	E28F008BVB@TSOP40 [CX1006]
E28F008BVT@TSOP40 [CX1006]	E28F008BXB@TSOP40 [CX1006]
E28F008BXT@TSOP40 [CX1006]	E28F008S3@TSOP40 [CX1006]
E28F008S5@TSOP40 [CX1006]	E28F008SA@TSOP40 [CX1006]
E28F008SA-L@TSOP40 [CX1006]	E28F008SC@TSOP40 [CX1006]
E28F010@TSOP32 [CX1002]	E28F016S3@TSOP40 [CX1006]
E28F016S5@TSOP40 [CX1006]	E28F016SA@TSOP56 [CX1055]
E28F016SC@TSOP40 [CX1006]	E28F016SV@TSOP56 [CX1055]
E28F020@TSOP32 [CX1002]	E28F128J3A@TSOP56 [CX1011]
E28F200B5B@TSOP48 [CX1004]	E28F200B5T@TSOP48 [CX1004]
E28F200BVB@TSOP56 [CX1055]	E28F200BVT@TSOP56 [CX1055]
E28F200BXB@TSOP56 [CX1055]	E28F200BXT@TSOP56 [CX1055]
E28F200CVB@TSOP48 [CX1004]	E28F200CVT@TSOP48 [CX1004]
E28F256@TSOP32 [CX1002]	E28F256A@TSOP32 [CX1002]
E28F320J3A@TSOP56 [CX1011]	E28F320J5@TSOP56 [CX1011]
E28F320J5A@TSOP56 [CX1011]	E28F400B5B@TSOP48 [CX1004]
E28F400B5T@TSOP48 [CX1004]	E28F400BLB@TSOP56 [CX1055]
E28F400BLT@TSOP56 [CX1055]	E28F400BVB@TSOP56 [CX1055]
E28F400BVT@TSOP56 [CX1055]	E28F400BXB@TSOP56 [CX1055]

E28F400BXT@TSOP56 [CX1055] E28F400CVB@TSOP48 [CX1004]  
E28F400CVT@TSOP48 [CX1004] E28F512@TSOP32 [CX1002]  
E28F640J3A@TSOP56 [CX1011] E28F800B5B@TSOP48 [CX1004]  
E28F800B5T@TSOP48 [CX1004] E28F800CEB@TSOP48 [CX1004]  
E28F800CET@TSOP48 [CX1004] E28F800CVB@TSOP48 [CX1004]  
E28F800CVT@TSOP48 [CX1004] E82802AA@TSOP40 [CX1006]  
E82802AB@TSOP40 [CX1006] E82802AC@TSOP40 [CX1006]  
F28F008SA@TSOP40(REVERSE) [CX1006]  
F28F010@TSOP32 [CX1002] F28F020@TSOP32 [CX1002]  
F28F020@TSOP32(REVERSE) [CX1002] F28F256@TSOP32 [CX1002]  
F28F256A@TSOP32 [CX1002] F28F512@TSOP32 [CX1002]  
G28F640J5@uBGA56 [CX5014] G28F640J5A@uBGA56 [CX5014]  
GE28F008B3BA@uBGA48 [CX5064] GE28F008B3TA@uBGA48 [CX5064]  
GE28F128K18C@FBGA56 [CX5035] GE28F128K3C@FBGA56 [CX5035]  
GE28F128L18B@VFPGA56 [CX5032] GE28F128L18T@VFPGA56 [CX5032]  
GE28F128L30B@VFPGA56 [CX5032] GE28F128L30T@VFPGA56 [CX5032]  
GE28F128W18BC(NO EFP)@VFPGA56 [CX5034]  
GE28F128W18BC@VFPGA56 [CX5034]  
GE28F128W18BD(NO EFP)@VFPGA56 [CX5035]  
GE28F128W18BD@VFPGA56 [CX5035]  
GE28F128W18TC(NO EFP)@VFPGA56 [CX5034]  
GE28F128W18TC@VFPGA56 [CX5034]  
GE28F128W18TD(NO EFP)@VFPGA56 [CX5035]  
GE28F128W18TD@VFPGA56 [CX5035]  
GE28F128W30BC(NO EFP)@VFPGA56 [CX5034]  
GE28F128W30BC@VFPGA56 [CX5034]  
GE28F128W30BD(NO EFP)@VFPGA56 [CX5035]  
GE28F128W30BD@VFPGA56 [CX5035]  
GE28F128W30TC(NO EFP)@VFPGA56 [CX5034]  
GE28F128W30TC@VFPGA56 [CX5034]  
GE28F128W30TD(NO EFP)@VFPGA56 [CX5035]  
GE28F128W30TD@VFPGA56 [CX5035] GE28F160B3B@uBGA48 [CX5064]  
GE28F160B3BC@VFPGA48 [CX5064] GE28F160B3BD@VFPGA48 [CX5064]  
GE28F160B3T@uBGA48 [CX5064] GE28F160B3TC@VFPGA48 [CX5064]  
GE28F160B3TD@VFPGA48 [CX5064] GE28F160C3BC@VFPGA48 [CX5064]  
GE28F160C3BD@VFPGA48 [CX5064] GE28F160C3TC@VFPGA48 [CX5064]  
GE28F160C3TD@VFPGA48 [CX5064] GE28F256K18C@FBGA79 [CX5036]  
GE28F256K3C@FBGA79 [CX5036] GE28F256L18B@VFPGA79 [CX5164]  
GE28F256L18T@VFPGA79 [CX5164] GE28F256L30B@VFPGA79 [CX5164]  
GE28F256L30T@VFPGA79 [CX5164] GE28F320B3BC@uBGA48 [CX5064]  
GE28F320B3BD@uBGA48 [CX5064] GE28F320B3TC@uBGA48 [CX5064]  
GE28F320B3TD@uBGA48 [CX5064] GE28F320C3BC@VFPGA48 [CX5064]  
GE28F320C3BD@VFPGA48 [CX5064] GE28F320C3TC@VFPGA48 [CX5064]  
GE28F320C3TD@VFPGA48 [CX5064] GE28F320J3A@VFPGA48 [CX5078]  
GE28F320J3C@VFPGA48 [CX5078]  
GE28F320W18BC(NO EFP)@VFPGA56 [CX5032]  
GE28F320W18BC@VFPGA56 [CX5032] GE28F320W18BD@VFPGA56 [CX5032]  
GE28F320W18BE@VFPGA56 [CX5032]  
GE28F320W18TC(NO EFP)@VFPGA56 [CX5032]  
GE28F320W18TC@VFPGA56 [CX5032] GE28F320W18TD@VFPGA56 [CX5032]  
GE28F320W18TE@VFPGA56 [CX5032]  
GE28F320W30BC(NO EFP)@VFPGA56 [CX5032]  
GE28F320W30BC@VFPGA56 [CX5032]  
GE28F320W30BD(NO EFP)@VFPGA56 [CX5032]  
GE28F320W30TC(NO EFP)@VFPGA56 [CX5032]  
GE28F320W30TC@VFPGA56 [CX5032]  
GE28F320W30TD(NO EFP)@VFPGA56 [CX5032]  
GE28F640B3BC@uBGA48 [CX5080] GE28F640B3TC@uBGA48 [CX5080]  
GE28F640C3BC@VFPGA48 [CX5080] GE28F640C3TC@VFPGA48 [CX5080]

GE28F640J3C@VFBGA48 [CX5078]                    GE28F640K18C@FBGA56 [CX5032]  
GE28F640K3C@FBGA56 [CX5032]                    GE28F640L18B@VFBGA56 [CX5032]  
GE28F640L18T@VFBGA56 [CX5032]                    GE28F640L30B@VFBGA56 [CX5032]  
GE28F640L30T@VFBGA56 [CX5032]  
GE28F640W18BC(NO EFP)@uBGA56 [CX5032]  
GE28F640W18BC@uBGA56 [CX5032]                    GE28F640W18BD@VFBGA56 [CX5032]  
GE28F640W18BE@VFBGA56 [CX5032]  
GE28F640W18TC(NO EFP)@uBGA56 [CX5032]  
GE28F640W18TC@uBGA56 [CX5032]                    GE28F640W18TD@VFBGA56 [CX5032]  
GE28F640W18TE@VFBGA56 [CX5032]  
GE28F640W30BC(NO EFP)@uBGA56 [CX5032]  
GE28F640W30BC@uBGA56 [CX5032]  
GE28F640W30BD(NO EFP)@uBGA56 [CX5032]  
GE28F640W30TC(NO EFP)@uBGA56 [CX5032]  
GE28F640W30TC@uBGA56 [CX5032]  
GE28F640W30TD(NO EFP)@uBGA56 [CX5032]  
GE28F800B3BA@uBGA48 [CX50UN]                    GE28F800B3TA@uBGA48 [CX50UN]  
GE28F800C3BA@VFBGA48 [CX50UN]                    GE28F800C3TA@VFBGA48 [CX50UN]  
GT28F016C3BA@FBGA48 [CX5064]                    GT28F016C3TA@FBGA48 [CX5064]  
GT28F032C3BA@FBGA48 [CX5064]                    GT28F032C3TA@FBGA48 [CX5064]  
GT28F128W30BC(NO EFP)@uBGA56 [CX5034]  
GT28F128W30BC@uBGA56 [CX5034]  
GT28F128W30BD(NO EFP)@uBGA56 [CX5035]  
GT28F128W30BD@uBGA56 [CX5035]  
GT28F128W30TC(NO EFP)@uBGA56 [CX5034]  
GT28F128W30TC@uBGA56 [CX5034]  
GT28F128W30TD(NO EFP)@uBGA56 [CX5035]  
GT28F128W30TD@uBGA56 [CX5035]                    GT28F160B3B@uBGA48 [CX5064]  
GT28F160B3BA@uBGA48 [CX5064]                    GT28F160B3T@uBGA48 [CX5064]  
GT28F160B3TA@uBGA48 [CX5064]                    GT28F160C3BA@FBGA48 [CX5064]  
GT28F160C3TA@FBGA48 [CX5064]                    GT28F320B3B@uBGA48 [CX5078]  
GT28F320B3BA@uBGA48 [CX5078]                    GT28F320B3T@uBGA48 [CX5078]  
GT28F320B3TA@uBGA48 [CX5078]                    GT28F320C3BA@FBGA48 [CX5078]  
GT28F320C3TA@FBGA48 [CX5078]                    GT28F800B3B@uBGA48 [CX50UN]  
GT28F800B3T@uBGA48 [CX50UN]                    JS28F00AM29EWH@TSOP56 [CX1055]  
JS28F00AM29EWS@TSOP56 [CX1055]                    JS28F00AM29EWL@TSOP56 [CX1055]  
JS28F00AM29EWS@TSOP56 [CX1055]                    JS28F00AP30BF@TSOP56 [CX1011]  
JS28F00AP30EF@TSOP56 [CX1011]                    JS28F00AP30TF@TSOP56 [CX1011]  
JS28F00AP33BF@TSOP56 [CX1011]                    JS28F00AP33EF@TSOP56 [CX1011]  
JS28F00AP33TF@TSOP56 [CX1011]                    JS28F128J3C@TSOP56 [CX1011]  
JS28F128J3D@TSOP56 [CX1011]                    JS28F128J3F@TSOP56 [CX1011]  
JS28F128P30B@TSOP56 [CX1011]                    JS28F128P30BF@TSOP56 [CX1011]  
JS28F128P30T@TSOP56 [CX1011]                    JS28F128P30TF@TSOP56 [CX1011]  
JS28F128P33B@TSOP56 [CX1011]                    JS28F128P33BF@TSOP56 [CX1011]  
JS28F128P33T@TSOP56 [CX1011]                    JS28F128P33TF@TSOP56 [CX1011]  
JS28F160B3BD@TSOP48 [CX1004]                    JS28F160B3TD@TSOP48 [CX1004]  
JS28F160C3BD@TSOP48 [CX1004]                    JS28F160C3TD@TSOP48 [CX1004]  
JS28F256J3C@TSOP56 [CX1011]                    JS28F256J3D@TSOP56 [CX1011]  
JS28F256J3F@TSOP56 [CX1011]                    JS28F256M29EWH@TSOP56 [CX1055]  
JS28F256M29EWS@TSOP56 [CX1055]                    JS28F256M29EWL(SD)@TSOP56 [CX1011]  
JS28F256M29EWL@TSOP56 [CX1055]                    JS28F256M29EWS@TSOP56 [CX1055]  
JS28F256P30B@TSOP56 [CX1011]                    JS28F256P30BF@TSOP56 [CX1011]  
JS28F256P30T@TSOP56 [CX1011]                    JS28F256P30TF@TSOP56 [CX1011]  
JS28F256P33B@TSOP56 [CX1011]                    JS28F256P33BF@TSOP56 [CX1011]  
JS28F256P33T@TSOP56 [CX1011]                    JS28F256P33TF@TSOP56 [CX1011]  
JS28F320B3BD@TSOP48 [CX1004]                    JS28F320B3TD@TSOP48 [CX1004]  
JS28F320C3BD@TSOP48 [CX1004]                    JS28F320C3TD@TSOP48 [CX1004]  
JS28F320J3C@TSOP56 [CX1011]                    JS28F320J3D@TSOP56 [CX1011]

JS28F320J3F@TSOP56 [CX1011] JS28F512M29AWH@FBGA56 [CX1055]  
JS28F512M29AWL@FBGA56 [CX1055] JS28F512M29EWH@TSOP56 [CX1055]  
JS28F512M29EWS@TSOP56 [CX1055] JS28F512M29EWL@TSOP56 [CX1055]  
JS28F512M29EWS@TSOP56 [CX1055] JS28F512P30BF@TSOP56 [CX1011]  
JS28F512P30EF@TSOP56 [CX1011] JS28F512P30TF@TSOP56 [CX1011]  
JS28F512P33BF@TSOP56 [CX1011] JS28F512P33EF@TSOP56 [CX1011]  
JS28F512P33TF@TSOP56 [CX1011] JS28F640J3C@TSOP56 [CX1011]  
JS28F640J3D@TSOP56 [CX1011] JS28F640J3F@TSOP56 [CX1011]  
JS28F640P30B@TSOP56 [CX1011] JS28F640P30BF@TSOP56 [CX1011]  
JS28F640P30T@TSOP56 [CX1011] JS28F640P30TF@TSOP56 [CX1011]  
JS28F640P33B@TSOP56 [CX1011] JS28F640P33BF@TSOP56 [CX1011]  
JS28F640P33T@TSOP56 [CX1011] JS28F640P33TF@TSOP56 [CX1011]  
JS28F800C3BD@TSOP48 [CX1004] JS28F800C3TD@TSOP48 [CX1004]  
JS48F4400P0TB00@TSOP56 [CX1011] JS48F4400P0VB00@TSOP56 [CX1011]  
JS48F4400P0VT00@TSOP56 [CX1011] JZ48F4000L0YBQ0@FBGA88 [CX5001]  
JZ48F4000L0YTQ0@FBGA88 [CX5001] JZ48F4000L0ZBQ0@FBGA88 [CX5001]  
JZ48F4000L0ZTQ0@FBGA88 [CX5001] M28F010 [CX0001]  
M28F010@PLCC32 [CX2032] M28F010@TSOP32 [CX1002]  
N28F001BN-B@PLCC32 [CX2032] N28F001BN-T@PLCC32 [CX2032]  
N28F001BX-B@PLCC32 [CX2032] N28F001BX-T@PLCC32 [CX2032]  
N28F010@PLCC32 [CX2032] N28F020@PLCC32 [CX2032]  
N28F256@PLCC32 [CX2032] N28F256A@PLCC32 [CX2032]  
N28F512@PLCC32 [CX2032] N29F040 [CX0001]  
N82802AA@PLCC32 [CX2032] N82802AB@PLCC32 [CX2032]  
N82802AC@PLCC32 [CX2032] NZ48F4000L0YBQ0@FBGA88 [CX5001]  
NZ48F4000L0YTQ0@FBGA88 [CX5001] NZ48F4000L0ZBQ0@FBGA88 [CX5001]  
NZ48F4000L0ZTQ0@FBGA88 [CX5001] P27011 [CX0001]  
P27128A [CX0001] P27128A@PLCC32 [CX2032]  
P27128B [CX0001] P27128B@PLCC32 [CX2032]  
P27256 [CX0001] P27256@PLCC32 [CX2032]  
P27512 [CX0001] P27513 [CX0001]  
P2764A [CX0001] P2764A@PLCC32 [CX2032]  
P27C011 [CX0001] P27C128 [CX0001]  
P27C128@PLCC32 [CX2032] P27C256 [CX0001]  
P27C256@PLCC32 [CX2032] P27C513 [CX0001]  
P27C64 [CX0001] P27C64@PLCC32 [CX2032]  
P28F001BX-B [CX0001] P28F001BX-T [CX0001]  
P28F002BCT [CX0001] P28F010 [CX0001]  
P28F020 [CX0001] P28F256 [CX0001]  
P28F256A [CX0001] P28F512 [CX0001]  
P87C64 [CX0001] P87C64@PLCC32 [CX2032]  
PA28F004S3@PSOP44 [CX1014] PA28F004S5@PSOP44 [CX1014]  
PA28F004SC@PSOP44 [CX1014] PA28F008S3@PSOP44 [CX1014]  
PA28F008S5@PSOP44 [CX1014] PA28F008SA@PSOP44 [CX1014]  
PA28F008SA-L@PSOP44 [CX1014] PA28F008SC@PSOP44 [CX1014]  
PA28F016S3@PSOP44 [CX1014] PA28F016S5@PSOP44 [CX1014]  
PA28F016SC@PSOP44 [CX1014] PA28F200B5B@PSOP44 [CX1014]  
PA28F200B5T@PSOP44 [CX1014] PA28F200BVB@PSOP44 [CX1014]  
PA28F200BVT@PSOP44 [CX1014] PA28F200BVB@PSOP44 [CX1014]  
PA28F200BXT@PSOP44 [CX1014] PA28F200BVB@PSOP44 [CX1014]  
PA28F200BXT@PSOP44 [CX1014] PA28F200BVB@PSOP44 [CX1014]  
PA28F400B5T@PSOP44 [CX1014] PA28F400B5B@PSOP44 [CX1014]  
PA28F400BLT@PSOP44 [CX1014] PA28F400BLB@PSOP44 [CX1014]  
PA28F400BVT@PSOP44 [CX1014] PA28F400BVB@PSOP44 [CX1014]  
PA28F400BXT@PSOP44 [CX1014] PA28F400BVB@PSOP44 [CX1014]  
PA28F400BXT@PSOP44 [CX1014] PA28F400BVB@PSOP44 [CX1014]  
PA28F800B5T@PSOP44 [CX1014] PA28F800B5B@PSOP44 [CX1014]  
PA28F800BVT@PSOP44 [CX1014] PA28F800BVB@PSOP44 [CX1014]  
PC28F00AM29EWH@FBGA64 [CX5074] PC28F00AM29EWS@FBGA64 [CX5074]  
PC28F00AM29EWL@FBGA64 [CX5074] PC28F00AM29EWS@FBGA64 [CX5074]  
PC28F00AP30BF@FBGA64 [CX5019] PC28F00AP30EF@FBGA64 [CX5019]

PC28F00AP30TF@FBGA64 [CX5019]      PC28F00AP33BF@FBGA64 [CX5019]  
PC28F00AP33EF@FBGA64 [CX5019]      PC28F00AP33TF@FBGA64 [CX5019]  
PC28F128G18F@FBGA64 [CX5019]      PC28F128J3C@FBGA64 [CX5004]  
PC28F128J3D@FBGA64 [CX5004]      PC28F128J3F@FBGA64 [CX5004]  
PC28F128P30B@EBGA64 [CX5004]      PC28F128P30BF@FBGA64 [CX5004]  
PC28F128P30T@EBGA64 [CX5004]      PC28F128P30TF@FBGA64 [CX5004]  
PC28F128P33B@EBGA64 [CX5019]      PC28F128P33BF@FBGA64 [CX5019]  
PC28F128P33T@EBGA64 [CX5019]      PC28F128P33TF@FBGA64 [CX5019]  
PC28F160C3BD@FBGA64 [CX5004]      PC28F160C3TD@FBGA64 [CX5004]  
PC28F256G18F@FBGA64 [CX5019]      PC28F256J3C@FBGA64 [CX5020]  
PC28F256J3D@FBGA64 [CX5020]      PC28F256J3F@FBGA64 [CX5004]  
PC28F256M29EWH@FBGA64 [CX5074]      PC28F256M29EWS@FBGA64 [CX5074]  
PC28F256M29EWL@FBGA64 [CX5074]      PC28F256M29EWLS@FBGA64 [CX5074]  
PC28F256P30B@EBGA64 [CX5004]      PC28F256P30BF@FBGA64 [CX5004]  
PC28F256P30T@EBGA64 [CX5004]      PC28F256P30TF@FBGA64 [CX5004]  
PC28F256P33B@EBGA64 [CX5004]      PC28F256P33BF@FBGA64 [CX5004]  
PC28F256P33T@EBGA64 [CX5004]      PC28F256P33TF@FBGA64 [CX5004]  
PC28F320B3BC@FBGA64 [CX5004]      PC28F320B3BD@FBGA64 [CX5004]  
PC28F320B3TC@FBGA64 [CX5004]      PC28F320B3TD@FBGA64 [CX5004]  
PC28F320C3BD@FBGA64 [CX5004]      PC28F320C3TD@FBGA64 [CX5004]  
PC28F320J3C@FBGA64 [CX5004]      PC28F320J3D@FBGA64 [CX5004]  
PC28F320J3F@FBGA64 [CX5004]      PC28F512G18F@FBGA64 [CX5019]  
PC28F512M29AWH@FBGA64 [CX5074]      PC28F512M29AWL@FBGA64 [CX5074]  
PC28F512M29EWH@FBGA64 [CX5074]      PC28F512M29EWS@FBGA64 [CX5074]  
PC28F512M29EWL@FBGA64 [CX5074]      PC28F512M29EWLS@FBGA64 [CX5074]  
PC28F512P30BF@FBGA64 [CX5019]      PC28F512P30EF@FBGA64 [CX5019]  
PC28F512P30TF@FBGA64 [CX5019]      PC28F512P33BF@FBGA64 [CX5019]  
PC28F512P33EF@FBGA64 [CX5019]      PC28F512P33TF@FBGA64 [CX5019]  
PC28F640J3C@FBGA64 [CX5004]      PC28F640J3D@FBGA64 [CX5004]  
PC28F640J3F@FBGA64 [CX5004]      PC28F640P30B@EBGA64 [CX5004]  
PC28F640P30BF@EBGA64 [CX5004]      PC28F640P30T@EBGA64 [CX5004]  
PC28F640P30TF@EBGA64 [CX5004]      PC28F640P33B@EBGA64 [CX5019]  
PC28F640P33BF@EBGA64 [CX5019]      PC28F640P33T@EBGA64 [CX5019]  
PC28F640P33TF@EBGA64 [CX5019]      PC28F800C3BD@FBGA64 [CX5004]  
PC28F800C3TD@FBGA64 [CX5004]      PC48F3300J0Z00S@FBGA64 [CX5004]  
PC48F4400P0TB00@FBGA64 [CX5004]      PC48F4400P0TB0E@FBGA64 [CX5004]  
PC48F4400P0VB00@FBGA64 [CX5004]      PC48F4400P0VB0E@FBGA64 [CX5004]  
PC48F4400P0VT00@FBGA64 [CX5004]      PF38F1020W0YBQ0@FBGA88 [CX5005]  
PF38F1020W0YBQ1@FBGA88 [CX5005]      PF38F1020W0YTQ0@FBGA88 [CX5005]  
PF38F1020W0YTQ1@FBGA88 [CX5005]      PF38F1030C0ZBL0@FBGA66 [CX5026]  
PF38F1030C0ZTL0@FBGA66 [CX5026]      PF38F1030W0YBQ2@FBGA88 [CX5005]  
PF38F1030W0YBQE@FBGA88 [CX5005]      PF38F1030W0YBQF@FBGA88 [CX5005]  
PF38F1030W0YBQE@FBGA88 [CX5005]      PF38F1030W0YBQF@FBGA88 [CX5005]  
PF38F1030W0YCQ3@FBGA88 [CX5005]      PF38F1030W0YBQF@FBGA88 [CX5005]  
PF38F1030W0YTQ2@FBGA88 [CX5005]      PF38F1030W0YCQE@FBGA88 [CX5005]  
PF38F1030W0YTQ2@FBGA88 [CX5005]      PF38F1030W0YTQE@FBGA88 [CX5005]  
PF38F1030W0YTQF@FBGA88 [CX5005]      PF38F1030W0YTQE@FBGA88 [CX5005]  
PF38F1030W0YTQF@FBGA88 [CX5005]      PF38F1030W0YUQ3@FBGA88 [CX5005]  
PF38F1030W0YUQE(HB)@FBGA88 [CX5005]      PF38F1030W0YUQ3@FBGA88 [CX5005]  
PF38F1030W0YUQE@FBGA88 [CX5005]      PF38F1030W0ZBQ0@FBGA88 [CX5005]  
PF38F1030W0ZBQ1@FBGA88 [CX5005]      PF38F2020W0ZBQ1@FBGA88 [CX5005]  
PF38F2020W0ZTQ1@FBGA88 [CX5005]      PF38F2030W0YBQ1@FBGA88 [CX5005]  
PF38F2030W0YBQ2@FBGA88 [CX5005]      PF38F2030W0YBQE@FBGA88 [CX5005]  
PF38F2030W0YBQF@FBGA88 [CX5005]      PF38F2030W0YBQE@FBGA88 [CX5005]  
PF38F2030W0YBQF@FBGA88 [CX5005]      PF38F2030W0YCQ3@FBGA88 [CX5005]  
PF38F2030W0YCQE@FBGA88 [CX5005]      PF38F2030W0YTQ1@FBGA88 [CX5005]  
PF38F2030W0YTQ2@FBGA88 [CX5005]      PF38F2030W0YTQ1@FBGA88 [CX5005]  
PF38F2030W0YTQ2@FBGA88 [CX5005]      PF38F2030W0YTQE@FBGA88 [CX5005]  
PF38F2030W0YTQF@FBGA88 [CX5005]      PF38F2030W0YTQE@FBGA88 [CX5005]  
PF38F2030W0YTQF@FBGA88 [CX5005]      PF38F2030W0YUQ3@FBGA88 [CX5005]  
PF38F2030W0YUQE(HB)@FBGA88 [CX5005]      PF38F2030W0YUQ3@FBGA88 [CX5005]  
PF38F2030W0YUQE@FBGA88 [CX5005]      PF38F2030W0ZBQ2@FBGA88 [CX5005]  
PF38F2030W0ZTQ2@FBGA88 [CX5005]      PF38F2040W0YBQ0@FBGA88 [CX5005]  
PF38F2040W0YCQ1@FBGA88 [CX5005]      PF38F2040W0YCQ3@FBGA88 [CX5005]  
PF38F2040W0YCQE@FBGA88 [CX5005]      PF38F2040W0YTQ0@FBGA88 [CX5005]



PF38F5060M0Y3DK@FBGA56 [CX5114] PF38F5066M0Y3DE@FBGA56 [CX5114]  
PF38F5070M0Y3DE@FBGA56 [CX5134] PF38F6070M0H0Q0@FBGA88 [CX5005]  
PF48F2000P0XBQ0@FBGA88 [CX5005] PF48F2000P0XTQ0@FBGA88 [CX5005]  
PF48F2000P0ZBQ0@FBGA88 [CX5005] PF48F2000P0ZTQ0@FBGA88 [CX5005]  
PF48F3000L0YBQ0@FBGA88 [CX5005] PF48F3000L0YTQ0@FBGA88 [CX5005]  
PF48F3000L0ZBQ0@FBGA88 [CX5005] PF48F3000L0ZTQ0@FBGA88 [CX5005]  
PF48F3000M0Y0QE@FBGA88 [CX5005] PF48F3000M0Y1QE@FBGA88 [CX5005]  
PF48F3000P0XBQ0@FBGA88 [CX5005] PF48F3000P0XTQ0@FBGA88 [CX5005]  
PF48F3000P0ZBQ0@FBGA88 [CX5005] PF48F3000P0ZBQE@FBGA88 [CX5005]  
PF48F3000P0ZTQ0@FBGA88 [CX5005] PF48F3000P0ZTQE@FBGA88 [CX5005]  
PF48F3000W0YBQ0@FBGA88 [CX5005] PF48F3000W0YTQ0@FBGA88 [CX5005]  
PF48F3000W0ZBQ0@FBGA88 [CX5005] PF48F3000W0ZTQ0@FBGA88 [CX5005]  
PF48F3300W0YBQ0@FBGA88 [CX5005] PF48F3300W0YDQ0@FBGA88 [CX5005]  
PF48F3300W0YTQ0@FBGA88 [CX5005] PF48F4000L0YBQ0@FBGA88 [CX5001]  
PF48F4000L0YTQ0@FBGA88 [CX5001] PF48F4000P0XBQ0@FBGA88 [CX5001]  
PF48F4000P0XTQ0@FBGA88 [CX5001] PF48F4000P0ZBQ0@FBGA88 [CX5001]  
PF48F4000P0ZBQE@FBGA88 [CX5001] PF48F4000P0ZTQ0@FBGA88 [CX5001]  
PF48F4000P0ZTQE@FBGA88 [CX5001] PF48F4040LVYBQ0(BEEP)@FBGA88 [CX5001]  
PF48F4040LVYBQ0(BP)@FBGA88 [CX5001]  
PF48F4040LVYTQ0(BEEP)@FBGA88 [CX5001]  
PF48F4040LVYTQ0(BP)@FBGA88 [CX5001]  
PF48F4400L0YDQ0@FBGA88 [CX5001] PF48F4400L0ZDQ0@FBGA88 [CX5001]  
PF48F4400P0TBQ0@FBGA88 [CX5001] PF48F4400P0VBQ0@FBGA88 [CX5001]  
PF48F4400P0VBQE@FBGA88 [CX5001] PF48F4400P0VTQ0@FBGA88 [CX5001]  
PH28F128L18B@VFPGA56 [CX5032] PH28F128L18T@VFPGA56 [CX5032]  
PH28F128L30B@VFPGA56 [CX5032] PH28F128L30T@VFPGA56 [CX5032]  
PH28F128W18BC(NO EFP)@VFPGA56 [CX5034]  
PH28F128W18BC@VFPGA56 [CX5034]  
PH28F128W18BD(NO EFP)@VFPGA56 [CX5035]  
PH28F128W18BD@VFPGA56 [CX5035]  
PH28F128W18TC(NO EFP)@VFPGA56 [CX5034]  
PH28F128W18TC@VFPGA56 [CX5034]  
PH28F128W18TD(NO EFP)@VFPGA56 [CX5035]  
PH28F128W18TD@VFPGA56 [CX5035] PH28F160B3BD@uBGA48 [CX5064]  
PH28F160B3TD@uBGA48 [CX5064] PH28F160C3BD@VFPGA48 [CX5064]  
PH28F160C3TD@VFPGA48 [CX5064] PH28F256L18B@VFPGA79 [CX5164]  
PH28F256L18T@VFPGA79 [CX5164] PH28F256L30B@VFPGA79 [CX5164]  
PH28F256L30T@VFPGA79 [CX5164] PH28F320B3BD@uBGA48 [CX5064]  
PH28F320B3TD@uBGA48 [CX5064] PH28F320C3BD@VFPGA48 [CX5064]  
PH28F320C3TD@VFPGA48 [CX5064] PH28F320W18BD@VFPGA56 [CX5032]  
PH28F320W18BE@VFPGA56 [CX5032] PH28F320W18TD@VFPGA56 [CX5032]  
PH28F320W18TE@VFPGA56 [CX5032] PH28F320W30BD@VFPGA56 [CX5032]  
PH28F320W30TD@VFPGA56 [CX5032] PH28F640C3BC@VFPGA48 [CX5080]  
PH28F640C3TC@VFPGA48 [CX5080] PH28F640L18B@VFPGA56 [CX5032]  
PH28F640L18T@VFPGA56 [CX5032] PH28F640L30B@VFPGA56 [CX5032]  
PH28F640L30T@VFPGA56 [CX5032] PH28F640W18BD@VFPGA56 [CX5032]  
PH28F640W18BE@VFPGA56 [CX5032] PH28F640W18TD@VFPGA56 [CX5032]  
PH28F640W18TE@VFPGA56 [CX5032] PH28F640W30BD@VFPGA56 [CX5032]  
PH28F640W30TD@VFPGA56 [CX5032] QB25F016S33B60@SOIC8 [CX1044#1]  
QB25F016S33T60@SOIC8 [CX1044#1] QB25F160S33B60@SOIC16 [CX1033#1]  
QB25F160S33T60@SOIC16 [CX1033#1] QB25F320S33B60@SOIC16 [CX1033#1]  
QB25F320S33T60@SOIC16 [CX1033#1] QB25F640S33B60@SOIC16 [CX1033#1]  
QB25F640S33T60@SOIC16 [CX1033#1] QH25F016S33B60@SOIC8 [CX1044#1]  
QH25F016S33T60@SOIC8 [CX1044#1] QH25F160S33B60@SOIC16 [CX1033#1]  
QH25F160S33T60@SOIC16 [CX1033#1] QH25F320S33B60@SOIC16 [CX1033#1]  
QH25F320S33T60@SOIC16 [CX1033#1] QH25F640S33B60@SOIC16 [CX1033#1]  
QH25F640S33T60@SOIC16 [CX1033#1] RC28F128J3A@FBGA64 [CX5004]  
RC28F128J3C@FBGA64 [CX5004] RC28F128J3D@FBGA64 [CX5004]



RC28F128J3F@FBGA64 [CX5004] RC28F128K18C@FBGA64 [CX5004]  
RC28F128K3C@FBGA64 [CX5004] RC28F128P30B@EBGA64 [CX5004]  
RC28F128P30BF@FBGA64 [CX5004] RC28F128P30T@EBGA64 [CX5004]  
RC28F128P30TF@FBGA64 [CX5004] RC28F128P33B@EBGA64 [CX5019]  
RC28F128P33BF@FBGA64 [CX5019] RC28F128P33T@EBGA64 [CX5019]  
RC28F128P33TF@FBGA64 [CX5019] RC28F160C3BA@FBGA64 [CX5004]  
RC28F160C3BC@FBGA64 [CX5004] RC28F160C3BD@FBGA64 [CX5004]  
RC28F160C3TA@FBGA64 [CX5004] RC28F160C3TC@FBGA64 [CX5004]  
RC28F160C3TD@FBGA64 [CX5004] RC28F256J3C@FBGA64 [CX5020]  
RC28F256J3D@FBGA64 [CX5020] RC28F256J3F@FBGA64 [CX5004]  
RC28F256K18C@FBGA64 [CX5020] RC28F256K3C@FBGA64 [CX5020]  
RC28F256M29EWH@FBGA64 [CX5074] RC28F256M29EWHS@FBGA64 [CX5074]  
RC28F256M29EWL@FBGA64 [CX5074] RC28F256M29EWLS@FBGA64 [CX5074]  
RC28F256P30B@EBGA64 [CX5004] RC28F256P30BF@FBGA64 [CX5004]  
RC28F256P30T@EBGA64 [CX5004] RC28F256P30TF@FBGA64 [CX5004]  
RC28F256P33B@EBGA64 [CX5004] RC28F256P33BF@FBGA64 [CX5004]  
RC28F256P33T@EBGA64 [CX5004] RC28F256P33TF@FBGA64 [CX5004]  
RC28F320B3BC@FBGA64 [CX5004] RC28F320B3BD@FBGA64 [CX5004]  
RC28F320B3TC@FBGA64 [CX5004] RC28F320B3TD@FBGA64 [CX5004]  
RC28F320C3BA@FBGA64 [CX5004] RC28F320C3BC@FBGA64 [CX5004]  
RC28F320C3BD@FBGA64 [CX5004] RC28F320C3TA@FBGA64 [CX5004]  
RC28F320C3TC@FBGA64 [CX5004] RC28F320C3TD@FBGA64 [CX5004]  
RC28F320J3A@FBGA64 [CX5004] RC28F320J3C@FBGA64 [CX5004]  
RC28F320J3D@FBGA64 [CX5004] RC28F320J3F@FBGA64 [CX5004]  
RC28F512M29EWH@FBGA64 [CX5074] RC28F512M29EWHS@FBGA64 [CX5074]  
RC28F512M29EWL@FBGA64 [CX5074] RC28F512M29EWLS@FBGA64 [CX5074]  
RC28F640C3BC@FBGA64 [CX5004] RC28F640C3TC@FBGA64 [CX5004]  
RC28F640J3A@FBGA64 [CX5004] RC28F640J3C@FBGA64 [CX5004]  
RC28F640J3D@FBGA64 [CX5004] RC28F640J3F@FBGA64 [CX5004]  
RC28F640K18C@FBGA64 [CX5004] RC28F640K3C@FBGA64 [CX5004]  
RC28F640P30B@EBGA64 [CX5004] RC28F640P30BF@EBGA64 [CX5004]  
RC28F640P30T@EBGA64 [CX5004] RC28F640P30TF@EBGA64 [CX5004]  
RC28F640P33B@EBGA64 [CX5019] RC28F640P33BF@EBGA64 [CX5019]  
RC28F640P33T@EBGA64 [CX5019] RC28F640P33TF@EBGA64 [CX5019]  
RC28F800C3BA@FBGA64 [CX5004] RC28F800C3BD@FBGA64 [CX5004]  
RC28F800C3TA@FBGA64 [CX5004] RC28F800C3TD@FBGA64 [CX5004]  
RC48F3300J0Z00S@FBGA64 [CX5004] RC48F4400P0TB00@FBGA64 [CX5004]  
RC48F4400P0TB0E@FBGA64 [CX5004] RC48F4400P0VB00@FBGA64 [CX5004]  
RC48F4400P0VB0E@FBGA64 [CX5004] RC48F4400P0VT00@FBGA64 [CX5004]  
RD28F1602C3B@FBGA66 [CX5005] RD28F1602C3B70@FBGA66 [CX5005]  
RD28F1602C3BD@FBGA66 [CX5005] RD28F1602C3T@FBGA66 [CX5005]  
RD28F1602C3T70@FBGA66 [CX5005] RD28F1602C3TD@FBGA66 [CX5005]  
RD28F1604C3B@FBGA66 [CX5026] RD28F1604C3BD@FBGA66 [CX5026]  
RD28F1604C3T@FBGA66 [CX5026] RD28F1604C3TD@FBGA66 [CX5026]  
RD28F3204C3B@FBGA66 [CX5026] RD28F3204C3T@FBGA66 [CX5026]  
RD28F3204W18B(NO EFP)@FBGA96 [CX5051]  
RD28F3204W18B@FBGA96 [CX5051]  
RD28F3204W18T(NO EFP)@FBGA96 [CX5051]  
RD28F3204W18T@FBGA96 [CX5051]  
RD28F3204W30B(NO EFP)@FBGA96 [CX5051]  
RD28F3204W30B@FBGA96 [CX5051]  
RD28F3204W30T(NO EFP)@FBGA96 [CX5051]  
RD28F3204W30T@FBGA96 [CX5051] RD28F3208C3B@FBGA66 [CX5051]  
RD28F3208C3T@FBGA66 [CX5051]  
RD28F3208W30B(NO EFP)@FBGA96 [CX5051]  
RD28F3208W30B@FBGA96 [CX5051]  
RD28F3208W30T(NO EFP)@FBGA96 [CX5051]  
RD28F3208W30T@FBGA96 [CX5051]  
RD28F6408W18B(NO EFP)@FBGA96 [CX5051]

RD28F6408W18B@FBGA96 [CX5051]  
RD28F6408W18T(NO EFP)@FBGA96 [CX5051]  
RD28F6408W18T@FBGA96 [CX5051]  
RD28F6408W30B(NO EFP)@FBGA96 [CX5051]  
RD28F6408W30B@FBGA96 [CX5051]  
RD28F6408W30T(NO EFP)@FBGA96 [CX5051]  
RD28F6408W30T@FBGA96 [CX5051]  
RD38F1010C0ZBL0@FBGA66 [CX5026]  
RD38F1010C0ZTL0@FBGA66 [CX5026]  
RD38F1010C0ZTL0@FBGA66 [CX5026]  
RD38F1020C0ZB@FBGA66 [CX5026]  
RD38F1020W0YBQ0@FBGA88 [CX5005]  
RD38F1020W0YTQ0@FBGA88 [CX5005]  
RD38F1030W0YBQ2@FBGA88 [CX5005]  
RD38F1030W0ZBQ0@FBGA88 [CX5005]  
RD38F2010W0YBQ0@FBGA88 [CX5005]  
RD38F2010W0ZBQ0@FBGA88 [CX5005]  
RD38F2020W0YBQ0@FBGA88 [CX5005]  
RD38F2020W0ZBQ0@FBGA88 [CX5005]  
RD38F2020W0ZTQ0@FBGA88 [CX5005]  
RD38F2030W0YBQ0@FBGA88 [CX5005]  
RD38F2030W0YBQ2@FBGA88 [CX5005]  
RD38F2030W0YBQF@FBGA88 [CX5005]  
RD38F2030W0YTQ1@FBGA88 [CX5005]  
RD38F2030W0YTQE@FBGA88 [CX5005]  
RD38F2030W0ZBQ0@FBGA88 [CX5005]  
RD38F2030W0ZBQ2@FBGA88 [CX5005]  
RD38F2030W0ZTQ1@FBGA88 [CX5005]  
RD38F2040W0YBQ0@FBGA88 [CX5005]  
RD38F2040W0YTQ0@FBGA88 [CX5005]  
RD38F2040W0ZBQ0@FBGA88 [CX5005]  
RD38F2040W0ZTQ0@FBGA88 [CX5005]  
RD38F2220WWYBQ0@FBGA88 [CX5005]  
RD38F2220WWYTQ0@FBGA88 [CX5005]  
RD38F2220WWZDQ0@FBGA88 [CX5005]  
RD38F2230WWYBQ0@FBGA88 [CX5005]  
RD38F2230WWYTQ0@FBGA88 [CX5005]  
RD38F2230WWZDQ0@FBGA88 [CX5005]  
RD38F2240WWYBQ0@FBGA88 [CX5005]  
RD38F2240WWYTQ0@FBGA88 [CX5005]  
RD38F2240WWZDQ0@FBGA88 [CX5005]  
RD38F2240WWZTQ0@FBGA88 [CX5005]  
RD38F3040L0YBQ1@FBGA88 [CX5005]  
RD38F3040L0YBQ2@FBGA88 [CX5005]  
RD38F3040L0YCQ0@FBGA88 [CX5005]  
RD38F3040L0YTQ1@FBGA88 [CX5005]  
RD38F3040L0YUQ0@FBGA88 [CX5005]  
RD38F3040L0ZTQ0@FBGA88 [CX5005]  
RD38F3050L0YBQ2@FBGA88 [CX5005]  
RD38F3050L0YTQ1@FBGA88 [CX5005]  
RD38F3050L0YUQ0@FBGA88 [CX5005]  
RD38F3050L0ZBQ1@FBGA88 [CX5005]  
RD38F3050L0ZTQ1@FBGA88 [CX5005]  
RD38F3340LLYDQ1@FBGA88 [CX5005]  
RD38F3350WWZDQ0@FBGA88 [CX5005]  
RD38F4050L0YBQ0@FBGA88 [CX5001]  
RD38F4050L0YBQ2@FBGA88 [CX5001]  
RD38F4050L0YTQ0@FBGA88 [CX5001]  
RD38F4050L0YTQ2@FBGA88 [CX5001]  
RD38F4050L0ZBQ0@FBGA88 [CX5001]  
RD38F4050L0ZTQ0@FBGA88 [CX5001]  
RD38F1010C0ZB@FBGA66 [CX5026]  
RD38F1010C0ZT@FBGA66 [CX5026]  
RD38F1010W0YTL0@FBGA67 [CX5005]  
RD38F1020C0ZT@FBGA66 [CX5026]  
RD38F1020W0YBQ1@FBGA88 [CX5005]  
RD38F1020W0YTQ1@FBGA88 [CX5005]  
RD38F1030W0YTQ2@FBGA88 [CX5005]  
RD38F1030W0ZTQ0@FBGA88 [CX5005]  
RD38F2010W0YTQ0@FBGA88 [CX5005]  
RD38F2010W0ZTQ0@FBGA88 [CX5005]  
RD38F2020W0YTQ0@FBGA88 [CX5005]  
RD38F2020W0ZBQ1@FBGA88 [CX5005]  
RD38F2020W0ZTQ1@FBGA88 [CX5005]  
RD38F2030W0YBQ1@FBGA88 [CX5005]  
RD38F2030W0YBQE@FBGA88 [CX5005]  
RD38F2030W0YTQ0@FBGA88 [CX5005]  
RD38F2030W0YTQ2@FBGA88 [CX5005]  
RD38F2030W0YTQF@FBGA88 [CX5005]  
RD38F2030W0ZBQ1@FBGA88 [CX5005]  
RD38F2030W0ZTQ0@FBGA88 [CX5005]  
RD38F2030W0ZTQ2@FBGA88 [CX5005]  
RD38F2040W0YBQ1@FBGA88 [CX5005]  
RD38F2040W0YTQ1@FBGA88 [CX5005]  
RD38F2040W0ZBQ1@FBGA88 [CX5005]  
RD38F2040W0ZTQ1@FBGA88 [CX5005]  
RD38F2220WWYDQ0@FBGA88 [CX5005]  
RD38F2220WWZBQ0@FBGA88 [CX5005]  
RD38F2220WWZTQ0@FBGA88 [CX5005]  
RD38F2230WWYDQ0@FBGA88 [CX5005]  
RD38F2230WWZBQ0@FBGA88 [CX5005]  
RD38F2230WWZTQ0@FBGA88 [CX5005]  
RD38F2240WWYDQ0@FBGA88 [CX5005]  
RD38F2240WWZBQ0@FBGA88 [CX5005]  
RD38F2240WWZDQ1@FBGA88 [CX5005]  
RD38F3040L0YBQ0@FBGA88 [CX5005]  
RD38F3040L0YBQ2@FBGA88 [CX5005]  
RD38F3040L0YTQ0@FBGA88 [CX5005]  
RD38F3040L0YTQ2@FBGA88 [CX5005]  
RD38F3040L0ZBQ0@FBGA88 [CX5005]  
RD38F3050L0YBQ1@FBGA88 [CX5005]  
RD38F3050L0YCQ0@FBGA88 [CX5005]  
RD38F3050L0YTQ2@FBGA88 [CX5005]  
RD38F3050L0ZBQ0@FBGA88 [CX5005]  
RD38F3050L0ZTQ0@FBGA88 [CX5005]  
RD38F3340LLYDQ0@FBGA88 [CX5005]  
RD38F3350LLZDQ0@FBGA88 [CX5005]  
RD38F3350WWZDQ1@FBGA88 [CX5005]  
RD38F4050L0YBQ1@FBGA88 [CX5001]  
RD38F4050L0YCQ0@FBGA88 [CX5001]  
RD38F4050L0YTQ1@FBGA88 [CX5001]  
RD38F4050L0YUQ0@FBGA88 [CX5001]  
RD38F4050L0ZBQ1@FBGA88 [CX5001]  
RD38F4050L0ZTQ1@FBGA88 [CX5001]

RD38F4055L0YBQ2@FBGA88 [CX5001] RD38F4055L0YTQ2@FBGA88 [CX5001]  
RD38F4055L0ZBQ0@FBGA88 [CX5001] RD38F4055L0ZTQ0@FBGA88 [CX5001]  
RD38F4350LLYBQ0@FBGA88 [CX5001] RD38F4350LLYBQ1@FBGA88 [CX5001]  
RD38F4350LLYTQ0@FBGA88 [CX5001] RD38F4350LLYTQ1@FBGA88 [CX5001]  
RD38F4450LLYBQ0@FBGA88 [CX5001] RD38F4450LLYTQ0@FBGA88 [CX5001]  
RD38F4450LVYBQ0@FBGA88 [CX5001] RD38F4450LVYBQ2@FBGA88 [CX5001]  
RD38F4450LVYTQ0@FBGA88 [CX5001] RD38F4450LVYTQ2@FBGA88 [CX5001]  
RD38F4455LLYBQ0@FBGA88 [CX50UN] RD38F4455LLYBQ1@FBGA88 [CX50UN]  
RD38F4455LLYBQ2@FBGA88 [CX50UN] RD38F4455LLYTQ0@FBGA88 [CX50UN]  
RD38F4455LLYTQ1@FBGA88 [CX50UN] RD38F4455LLYTQ2@FBGA88 [CX50UN]  
RD48F2000L0YBQ0@FBGA88 [CX5005] RD48F2000L0YTQ0@FBGA88 [CX5005]  
RD48F2000L0ZBQ0@FBGA88 [CX5005] RD48F2000L0ZTQ0@FBGA88 [CX5005]  
RD48F2000P0XBQ0@FBGA88 [CX5005] RD48F2000P0XTQ0@FBGA88 [CX5005]  
RD48F2000P0ZBQ0@FBGA88 [CX5005] RD48F2000P0ZTQ0@FBGA88 [CX5005]  
RD48F2000W0YBQ0@FBGA88 [CX5005] RD48F2000W0YTQ0@FBGA88 [CX5005]  
RD48F2000W0ZBQ0@FBGA88 [CX5005] RD48F2000W0ZTQ0@FBGA88 [CX5005]  
RD48F2100W0YBQ0@FBGA88 [CX5005] RD48F2100W0YDQE@FBGA88 [CX5005]  
RD48F2100W0YTQ0@FBGA88 [CX5005] RD48F2200W0YBQ0@FBGA88 [CX5005]  
RD48F2200W0YDQ0@FBGA88 [CX5005] RD48F2200W0YTQ0@FBGA88 [CX5005]  
RD48F2200W0ZBQ0@FBGA88 [CX5005] RD48F2200W0ZDQ0@FBGA88 [CX5005]  
RD48F2200W0ZTQ0@FBGA88 [CX5005] RD48F3000L0YBQ0@FBGA88 [CX5005]  
RD48F3000L0YTQ0@FBGA88 [CX5005] RD48F3000L0ZBQ0@FBGA88 [CX5005]  
RD48F3000L0ZTQ0@FBGA88 [CX5005] RD48F3000P0XBQ0@FBGA88 [CX5005]  
RD48F3000P0XTQ0@FBGA88 [CX5005] RD48F3000P0ZBQ0@FBGA88 [CX5005]  
RD48F3000P0ZBQE@FBGA88 [CX5005] RD48F3000P0ZTQ0@FBGA88 [CX5005]  
RD48F3000P0ZTQE@FBGA88 [CX5005] RD48F3000W0YBQ0@FBGA88 [CX5005]  
RD48F3000W0YTQ0@FBGA88 [CX5005] RD48F3000W0ZBQ0@FBGA88 [CX5005]  
RD48F3000W0ZTQ0@FBGA88 [CX5005] RD48F3300L0YDQ0@FBGA88 [CX5005]  
RD48F3300L0ZDQ0@FBGA88 [CX5005] RD48F3300W0YBQ0@FBGA88 [CX5005]  
RD48F3300W0YDQ0@FBGA88 [CX5005] RD48F3300W0YTQ0@FBGA88 [CX5005]  
RD48F4000L0YBQ0@FBGA88 [CX5001] RD48F4000L0YTQ0@FBGA88 [CX5001]  
RD48F4000P0XBQ0@FBGA88 [CX5001] RD48F4000P0XTQ0@FBGA88 [CX5001]  
RD48F4000P0ZBQ0@FBGA88 [CX5001] RD48F4000P0ZTQ0@FBGA88 [CX5001]  
RD48F4040LVYBQ0(BEEP)@FBGA88 [CX5001]  
RD48F4040LVYBQ0(BP)@FBGA88 [CX5001]  
RD48F4040LVYTQ0(BEEP)@FBGA88 [CX5001]  
RD48F4040LVYTQ0(BP)@FBGA88 [CX5001]  
RD48F4040LVZBQ0(BEEP)@FBGA88 [CX5001]  
RD48F4040LVZBQ0(BP)@FBGA88 [CX5001]  
RD48F4040LVZTQ0(BEEP)@FBGA88 [CX5001]  
RD48F4040LVZTQ0(BP)@FBGA88 [CX5001]  
RD48F4400L0YDQ0@FBGA88 [CX5001] RD48F4400L0ZDN0@FBGA88 [CX5001]  
RD48F4400L0ZDQ0@FBGA88 [CX5001] RD48F4400P0TBQ0@FBGA88 [CX5001]  
RD48F4400P0VBQ0@FBGA88 [CX5001] RD48F4400P0VTQ0@FBGA88 [CX5001]  
RD48F4440LVYBQ0@FBGA88 [CX5001] RD48F4444LLZBB0@FBGA103 [CX5005]  
RD48F4444LVYBB0@FBGA103 [CX50UN] RF48F4400P0VBQE@FBGA88 [CX5001]  
TB28F004S3@PSOP44 [CX1014] TB28F004S5@PSOP44 [CX1014]  
TB28F004SC@PSOP44 [CX1014] TB28F008S3@PSOP44 [CX1014]  
TB28F008S5@PSOP44 [CX1014] TB28F008SA@PSOP44 [CX1014]  
TB28F008SA-L@PSOP44 [CX1014] TB28F008SC@PSOP44 [CX1014]  
TB28F016S3@PSOP44 [CX1014] TB28F016S5@PSOP44 [CX1014]  
TB28F016SC@PSOP44 [CX1014] TB28F200B5B@PSOP44 [CX1014]  
TB28F200B5T@PSOP44 [CX1014] TB28F200BVB@PSOP44 [CX1014]  
TB28F200BVT@PSOP44 [CX1014] TB28F200BXB@PSOP44 [CX1014]  
TB28F200BXT@PSOP44 [CX1014] TB28F400B5B@PSOP44 [CX1014]  
TB28F400B5T@PSOP44 [CX1014] TB28F400BVB@PSOP44 [CX1014]  
TB28F400BVT@PSOP44 [CX1014] TB28F400BXB@PSOP44 [CX1014]  
TB28F400BXT@PSOP44 [CX1014] TB28F800B5B@PSOP44 [CX1014]  
TB28F800B5T@PSOP44 [CX1014] TB28F800BVB@PSOP44 [CX1014]

TB28F800BVT@PSOP44 [CX1014]  
TE28F002BET@TSOP40 [CX1006]  
TE28F002BVT@TSOP40 [CX1006]  
TE28F002BXT@TSOP40 [CX1006]  
TE28F004BET@TSOP40 [CX1006]  
TE28F004BVT@TSOP40 [CX1006]  
TE28F004BXT@TSOP40 [CX1006]  
TE28F004S5@TSOP40 [CX1006]  
TE28F008B3B@TSOP40 [CX1006]  
TE28F008B3T@TSOP40 [CX1006]  
TE28F008BEB@TSOP40 [CX1006]  
TE28F008BVB@TSOP40 [CX1006]  
TE28F008C3BA@TSOP40 [CX1006]  
TE28F008S3@TSOP40 [CX1006]  
TE28F008SA@TSOP40 [CX1006]  
TE28F008SC@TSOP40 [CX1006]  
TE28F016B3T@TSOP40 [CX1006]  
TE28F016C3TA@TSOP40 [CX1006]  
TE28F016S5@TSOP40 [CX1006]  
TE28F128J3C@TSOP56 [CX1011]  
TE28F128J3F@TSOP56 [CX1011]  
TE28F128P30BF@TSOP56 [CX1011]  
TE28F128P30TF@TSOP56 [CX1011]  
TE28F128P33BF@TSOP56 [CX1011]  
TE28F128P33TF@TSOP56 [CX1011]  
TE28F160B3BA@TSOP48 [CX1004]  
TE28F160B3BD@TSOP48 [CX1004]  
TE28F160B3TA@TSOP48 [CX1004]  
TE28F160B3TD@TSOP48 [CX1004]  
TE28F160C3BC@TSOP48 [CX1004]  
TE28F160C3TA@TSOP48 [CX1004]  
TE28F160C3TD@TSOP48 [CX1004]  
TE28F160F3T@TSOP56 [CX1055]  
TE28F160S5@TSOP56 [CX1055]  
TE28F200B5T@TSOP48 [CX1004]  
TE28F200BVT@TSOP56 [CX1055]  
TE28F200BXT@TSOP56 [CX1055]  
TE28F200CET@TSOP56 [CX1055]  
TE28F200CVT@TSOP48 [CX1004]  
TE28F256J3D@TSOP56 [CX1011]  
TE28F256P30B@TSOP56 [CX1011]  
TE28F256P30T@TSOP56 [CX1011]  
TE28F256P33B@TSOP56 [CX1011]  
TE28F256P33T@TSOP56 [CX1011]  
TE28F320B3B@TSOP48 [CX1004]  
TE28F320B3BC@TSOP48 [CX1004]  
TE28F320B3T@TSOP48 [CX1004]  
TE28F320B3TC@TSOP48 [CX1004]  
TE28F320C3BA@TSOP48 [CX1004]  
TE28F320C3BD@TSOP48 [CX1004]  
TE28F320C3TC@TSOP48 [CX1004]  
TE28F320J3C@TSOP56 [CX1011]  
TE28F320J3F@TSOP56 [CX1011]  
TE28F400B3T@TSOP48 [CX1004]  
TE28F400B5T@TSOP48 [CX1004]  
TE28F400BVT@TSOP56 [CX1055]  
TE28F400BXT@TSOP56 [CX1055]  
TE28F400CET@TSOP48 [CX1004]  
TE28F400CVT@TSOP48 [CX1004]  
TE28F002BEB@TSOP40 [CX1006]  
TE28F002BVB@TSOP40 [CX1006]  
TE28F002BXB@TSOP40 [CX1006]  
TE28F004BEB@TSOP40 [CX1006]  
TE28F004BVB@TSOP40 [CX1006]  
TE28F004BXB@TSOP40 [CX1006]  
TE28F004S3@TSOP40 [CX1006]  
TE28F004SC@TSOP40 [CX1006]  
TE28F008B3BA@TSOP40 [CX1006]  
TE28F008B3TA@TSOP40 [CX1006]  
TE28F008BET@TSOP40 [CX1006]  
TE28F008BVT@TSOP40 [CX1006]  
TE28F008C3TA@TSOP40 [CX1006]  
TE28F008S5@TSOP40 [CX1006]  
TE28F008SA-L@TSOP40 [CX1006]  
TE28F016B3B@TSOP40 [CX1006]  
TE28F016C3BA@TSOP40 [CX1006]  
TE28F016S3@TSOP40 [CX1006]  
TE28F016SC@TSOP40 [CX1006]  
TE28F128J3D@TSOP56 [CX1011]  
TE28F128P30B@TSOP56 [CX1011]  
TE28F128P30T@TSOP56 [CX1011]  
TE28F128P33B@TSOP56 [CX1011]  
TE28F128P33T@TSOP56 [CX1011]  
TE28F160B3B@TSOP48 [CX1004]  
TE28F160B3BC@TSOP48 [CX1004]  
TE28F160B3T@TSOP48 [CX1004]  
TE28F160B3TC@TSOP48 [CX1004]  
TE28F160C3BA@TSOP48 [CX1004]  
TE28F160C3BD@TSOP48 [CX1004]  
TE28F160C3TC@TSOP48 [CX1004]  
TE28F160F3B@TSOP56 [CX1055]  
TE28F160S3@TSOP56 [CX1055]  
TE28F200B5B@TSOP48 [CX1004]  
TE28F200BVB@TSOP56 [CX1055]  
TE28F200BXB@TSOP56 [CX1055]  
TE28F200CEB@TSOP56 [CX1055]  
TE28F200CVB@TSOP48 [CX1004]  
TE28F256J3C@TSOP56 [CX1011]  
TE28F256J3F@TSOP56 [CX1011]  
TE28F256P30BF@TSOP56 [CX1011]  
TE28F256P30TF@TSOP56 [CX1011]  
TE28F256P33BF@TSOP56 [CX1011]  
TE28F256P33TF@TSOP56 [CX1011]  
TE28F320B3BA@TSOP48 [CX1004]  
TE28F320B3BD@TSOP48 [CX1004]  
TE28F320B3TA@TSOP48 [CX1004]  
TE28F320B3TD@TSOP48 [CX1004]  
TE28F320C3BC@TSOP48 [CX1004]  
TE28F320C3TA@TSOP48 [CX1004]  
TE28F320C3TD@TSOP48 [CX1004]  
TE28F320J3D@TSOP56 [CX1011]  
TE28F400B3B@TSOP48 [CX1004]  
TE28F400B5B@TSOP48 [CX1004]  
TE28F400BVB@TSOP56 [CX1055]  
TE28F400BXB@TSOP56 [CX1055]  
TE28F400CEB@TSOP48 [CX1004]  
TE28F400CVB@TSOP48 [CX1004]  
TE28F640B3BC@TSOP48 [CX1004]

TE28F640B3TC@TSOP48 [CX1004]	TE28F640C3BC@TSOP48 [CX1004]
TE28F640C3TC@TSOP48 [CX1004]	TE28F640J3C@TSOP56 [CX1011]
TE28F640J3D@TSOP56 [CX1011]	TE28F640J3F@TSOP56 [CX1011]
TE28F640P30B@TSOP56 [CX1011]	TE28F640P30T@TSOP56 [CX1011]
TE28F640P33B@TSOP56 [CX1011]	TE28F640P33T@TSOP56 [CX1011]
TE28F800B3B@TSOP48 [CX1004]	TE28F800B3BA@TSOP48 [CX1004]
TE28F800B3T@TSOP48 [CX1004]	TE28F800B3TA@TSOP48 [CX1004]
TE28F800B5B@TSOP48 [CX1004]	TE28F800B5T@TSOP48 [CX1004]
TE28F800C3BA@TSOP48 [CX1004]	TE28F800C3BD@TSOP48 [CX1004]
TE28F800C3TA@TSOP48 [CX1004]	TE28F800C3TD@TSOP48 [CX1004]
TE28F800CEB@TSOP48 [CX1004]	TE28F800CET@TSOP48 [CX1004]
TE28F800CVB@TSOP48 [CX1004]	TE28F800CVT@TSOP48 [CX1004]
TE28F800F3B@TSOP56 [CX1055]	TE28F800F3T@TSOP56 [CX1055]
TE48F4400P0TB00@TSOP56 [CX1011]	TE48F4400P0VB00@TSOP56 [CX1011]
TE48F4400P0VT00@TSOP56 [CX1011]	

## PLD

5C031 [CX0001]	5C031@PLCC20 [CX2020]
5C032 [CX0001]	5C032@PLCC20 [CX2020]
5C090 [CX0001]	5C090@PLCC44 [CX2044]
5C180@PLCC68 [CX2068]	85C090 [CX0001]
85C090@PLCC44 [CX2044]	85C220 [CX0001]
85C220@PLCC20 [CX2020]	IPLD910 [CX0001]
IPLD910@PLCC44 [CX2044]	

## MICROCONTROLLER

8744 [CX0001]	8744H [CX0001]
8751 [CX0001]	8751H [CX0001]
8751H-8 [CX0001]	87C151SA [CX0001]
87C151SA@PLCC44 [CX2044]	87C151SB [CX0001]
87C151SB@PLCC44 [CX2044]	87C251SA [CX0001]
87C251SA@PLCC44 [CX2044]	87C251SB [CX0001]
87C251SB@PLCC44 [CX2044]	87C251SP [CX0001]
87C251SP@PLCC44 [CX2044]	87C251SQ [CX0001]
87C251SQ@PLCC44 [CX2044]	87C51 [CX0001]
87C51@PLCC44 [CX2044]	87C51@TQFP44 [CX3002]
87C51FA [CX0001]	87C51FA@PLCC44 [CX2044]
87C51FA@TQFP44 [CX3002]	87C51FB [CX0001]
87C51FB@PLCC44 [CX2044]	87C51FB@TQFP44 [CX3002]
87C51FC [CX0001]	87C51FC@PLCC44 [CX2044]
87C51FC@TQFP44 [CX3003]	87C51RA [CX0001]
87C51RA@PLCC44 [CX2044]	87C51RA@TQFP44 [CX3002]
87C51RB [CX0001]	87C51RB@PLCC44 [CX2044]
87C51RB@TQFP44 [CX3002]	87C51RC [CX0001]
87C51RC@PLCC44 [CX2044]	87C51RC@TQFP44 [CX3003]
87C52 [CX0001]	87C52@PLCC44 [CX2044]
87C52@TQFP44 [CX3002]	87C54 [CX0001]
87C54@PLCC44 [CX2044]	87C54@TQFP44 [CX3003]
87C58 [CX0001]	87C58@PLCC44 [CX2044]
87C58@TQFP44 [CX3003]	87L51FA [CX0001]
87L51FA@PLCC44 [CX2044]	87L51FA@TQFP44 [CX3002]
87L51FB [CX0001]	87L51FB@PLCC44 [CX2044]
87L51FB@TQFP44 [CX3002]	87L51FC@PLCC44 [CX2044]
87L51FC@TQFP44 [CX3003]	87L52 [CX0001]
87L52@PLCC44 [CX2044]	87L52@TQFP44 [CX3002]
87L54@PLCC44 [CX2044]	87L54@TQFP44 [CX3003]

87L58@PLCC44 [CX2044]  
D8748 [CX0001]  
D8749 [CX0001]  
D8751 [CX0001]  
D8751H-8 [CX0001]  
MD8748H [CX0001]  
MD8749H [CX0001]  
P8748H [CX0001]  
P8749H [CX0001]

87L58@TQFP44 [CX3003]  
D8748H [CX0001]  
D8749H [CX0001]  
D8751H [CX0001]  
MD8748 [CX0001]  
MD8749 [CX0001]  
P8748 [CX0001]  
P8749 [CX0001]

## INTELSIL

### E (E) PROM/FRAM/NVRAM

HS-6617RH [CX0001]  
HS-6617RH-T [CX0001]  
HS-6664RH [CX0001]  
HS-6664RH-T [CX0001]  
HS-6883RH [CX0001]  
HS-6883RH-T [CX0001]

HS-6617RH@SOIC24 [CX1033]  
HS-6617RH-T@SOIC24 [CX1033]  
HS-6664RH@SOIC28 [CX1033]  
HS-6664RH-T@SOIC28 [CX1033]  
HS-6883RH@SOIC24 [CX1033]  
HS-6883RH-T@SOIC24 [CX1033]

## INTERSIL

### E (E) PROM/FRAM/NVRAM

X4043 [CX0001]  
X4043@SOIC8 [CX1045]  
X4045@MSOP8 [CX1000]

X4043@MSOP8 [CX1000]  
X4045 [CX0001]  
X4045@SOIC8 [CX1045]

## IR

### MICROCONTROLLER

IRMCK171@QFP48 [CX3091]  
IRMCK171@QFP48(LeftDown) [CX3091-A]  
IRMCK311@QFP64(LefeUp) [CX3105]  
IRMCK341@QFP64(LefeUp) [CX3096]  
IRMCK343@QFP64(LefeUp) [CX3096]

IRMCK341@QFP64 [CX3096-A]  
IRMCK343@QFP64 [CX3096-A]

## ISSI

### E (E) PROM/FRAM/NVRAM

IS24C01 [CX0001]  
IS24C01@SOIC8 [CX1045]  
IS24C01B [CX0001]  
IS24C01B@SOIC8 [CX1045]  
IS24C01C [CX0001]  
IS24C01C@SOIC8 [CX1045]  
IS24C02 [CX0001]  
IS24C02@SOIC8 [CX1045]  
IS24C02A [CX0001]  
IS24C02A@MSOP8 [CX1015]  
IS24C02A@TSSOP8 [CX1059]  
IS24C02B@DFN8

IS24C01@MSOP8 [CX1015]  
IS24C01@TSSOP8 [CX1059]  
IS24C01B@MSOP8 [CX1015]  
IS24C01B@TSSOP8 [CX1059]  
IS24C01C@MSOP8 [CX1015]  
IS24C01C@TSSOP8 [CX1059]  
IS24C02@MSOP8 [CX1015]  
IS24C02@TSSOP8 [CX1059]  
IS24C02A@DFN8  
IS24C02A@SOIC8 [CX1045]  
IS24C02B [CX0001]  
IS24C02B@MSOP8 [CX1015]

IS24C02B@SOIC8 [CX1045]  
IS24C02C [CX0001]  
IS24C02C@MSOP8 [CX1015]  
IS24C02C@TSSOP8 [CX1059]  
IS24C02E@DFN8  
IS24C02E@SOIC8 [CX1045]  
IS24C04 [CX0001]  
IS24C04@SOIC8 [CX1045]  
IS24C04A [CX0001]  
IS24C04A@MSOP8 [CX1015]  
IS24C04A@TSSOP8 [CX1059]  
IS24C04B@DFN8  
IS24C04B@SOIC8 [CX1045]  
IS24C08 [CX0001]  
IS24C08@SOIC8 [CX1045]  
IS24C08A [CX0001]  
IS24C08A@MSOP8 [CX1015]  
IS24C08A@TSSOP8 [CX1059]  
IS24C08B@DFN8  
IS24C08B@SOIC8 [CX1045]  
IS24C128 [CX0001]  
IS24C128@TSSOP14 [CX1000]  
IS24C128B@SOIC8 [CX1045]  
IS24C16 [CX0001]  
IS24C16@SOIC8 [CX1045]  
IS24C16A [CX0001]  
IS24C16A@SOIC8 [CX1045]  
IS24C16B [CX0001]  
IS24C16B@SOIC8 [CX1045]  
IS24C256 [CX0001]  
IS24C256@TSSOP14 [CX1000]  
IS24C256A@SOIC8 [CX1045]  
IS24C256C [CX0001]  
IS24C256C@TSSOP14 [CX1000]  
IS24C32@SOIC8 [CX1045]  
IS24C32A [CX0001]  
IS24C32A@SOIC8 [CX1045]  
IS24C32B [CX0001]  
IS24C32B@TSSOP8 [CX1059]  
IS24C32C@DFN8 [CX4002]  
IS24C32C@SOIC8 [CX1045]  
IS24C64 [CX0001]  
IS24C64@TSSOP8 [CX1059]  
IS24C64A@MSOP8 [CX1015]  
IS24C64A@TSSOP8 [CX1059]  
IS24C64B@SOIC8 [CX1045]  
IS24C64C [CX0001]  
IS24C64C@SOIC8 [CX1045]  
IS24L128 [CX0001]  
IS24L128@SOIC8(200mil) [CX1044]  
IS24L256@SOIC8(150mil) [CX1045]  
IS25C01 [CX0001]  
IS25C01@TSSOP8 [CX1059]  
IS25C02@SOIC8 [CX1045]  
IS25C04 [CX0001]  
IS25C04@TSSOP8  
IS25C08@SOIC8 [CX1045]  
IS25C128@SOIC8 [CX1045]  
IS25C128A@SOIC8 [CX1045]  
IS24C02B@TSSOP8 [CX1059]  
IS24C02C@DFN8  
IS24C02C@SOIC8 [CX1045]  
IS24C02E [CX0001]  
IS24C02E@MSOP8 [CX1015]  
IS24C02E@TSSOP8 [CX1059]  
IS24C04@MSOP8 [CX1015]  
IS24C04@TSSOP8 [CX1059]  
IS24C04A@DFN8  
IS24C04A@SOIC8 [CX1045]  
IS24C04B [CX0001]  
IS24C04B@MSOP8 [CX1015]  
IS24C04B@TSSOP8 [CX1059]  
IS24C08@MSOP8 [CX1015]  
IS24C08@TSSOP8 [CX1059]  
IS24C08A@DFN8  
IS24C08A@SOIC8 [CX1045]  
IS24C08B [CX0001]  
IS24C08B@MSOP8 [CX1015]  
IS24C08B@TSSOP8 [CX1059]  
IS24C128@SOIC8 [CX1045]  
IS24C128B [CX0001]  
IS24C128B@TSSOP14 [CX1000]  
IS24C16@MSOP8 [CX1015]  
IS24C16@TSSOP8 [CX1059]  
IS24C16A@MSOP8 [CX1015]  
IS24C16A@TSSOP8 [CX1059]  
IS24C16B@MSOP8 [CX1015]  
IS24C16B@TSSOP8 [CX1059]  
IS24C256@SOIC8 [CX1045]  
IS24C256A [CX0001]  
IS24C256A@TSSOP14 [CX1000]  
IS24C256C@SOIC8 [CX1045]  
IS24C32 [CX0001]  
IS24C32@TSSOP8 [CX1059]  
IS24C32A@MSOP8 [CX1015]  
IS24C32A@TSSOP8 [CX1059]  
IS24C32B@SOIC8 [CX1045]  
IS24C32C [CX0001]  
IS24C32C@MSOP8 [CX1015]  
IS24C32C@TSSOP8 [CX1059]  
IS24C64@SOIC8 [CX1045]  
IS24C64A [CX0001]  
IS24C64A@SOIC8 [CX1045]  
IS24C64B [CX0001]  
IS24C64B@TSSOP8 [CX1059]  
IS24C64C@MSOP8 [CX1015]  
IS24C64C@TSSOP8 [CX1059]  
IS24L128@SOIC8(150mil) [CX1045]  
IS24L256 [CX0001]  
IS24L256@SOIC8(200mil) [CX1044]  
IS25C01@SOIC8 [CX1045]  
IS25C02 [CX0001]  
IS25C02@TSSOP8 [CX1059]  
IS25C04@SOIC8 [CX1045]  
IS25C08 [CX0001]  
IS25C08@TSSOP8 [CX1059]  
IS25C128@TSSOP8 [CX1059]  
IS25C128A@TSSOP8 [CX1059]

IS25C16 [CX0001] IS25C16@SOIC8 [CX1045]  
IS25C16@TSSOP8 [CX1059] IS25C256@SOIC8 [CX1045]  
IS25C256@TSSOP8 [CX1059] IS25C256A@SOIC8 [CX1045]  
IS25C256A@TSSOP8 [CX1059] IS25C32A [CX0001]  
IS25C32A@SOIC8 [CX1045] IS25C32A@TSSOP8 [CX1059]  
IS25C32B [CX0001] IS25C32B@SOIC8 [CX1045]  
IS25C32B@TSSOP8 [CX1059] IS25C64A [CX0001]  
IS25C64A@SOIC8 [CX1045] IS25C64A@TSSOP8 [CX1059]  
IS25C64B [CX0001] IS25C64B@SOIC8 [CX1045]  
IS25C64B@TSSOP8 [CX1059] IS25LD010@SOIC8 [CX1045#1]  
IS25LD010@TSSOP8 [CX1059#3] IS25LD010@WSIN8 [CX4005#1]  
IS25LD020@SOIC8 [CX1045#1] IS25LD020@TSSOP8 [CX1059#3]  
IS25LD020@WSIN8 [CX4005#1] IS25LD040@SOIC8 [CX1045#1]  
IS25LD040@WSIN8 [CX4005#1] IS25LD040-B8 [CX1044#1]  
IS25LD256C@SOIC8 [CX1045#1] IS25LD256C@TSSOP8 [CX1059#3]  
IS25LD256C@WSON8 [CX4005#1] IS25LD512@SOIC8 [CX1045#1]  
IS25LD512@TSSOP8 [CX1059#3] IS25LD512@WSON8 [CX4005#1]  
IS25LQ032C@SOIC8 [CX1044#1] IS25LQ032C@WSON8 [CX4006#1]  
IS25WD020@SOIC8(150mil) [CX1045#1] IS25WD020@WSON8 [CX4005#1]  
IS25WD020@SOIC8(200mil) [CX1044#1]  
IS25WD020@VVSOP8 [CX1045#1]  
IS25WD040@SOIC8(150mil) [CX1045#1] IS25WD040@WSON8 [CX4005#1]  
IS25WD040@SOIC8(200mil) [CX1044#1]  
IS25WD040@VVSOP8 [CX1045#1]  
IS27C010 [CX0001] IS27C010@PLCC32 [CX2032]  
IS27C010@TSOP32 [CX1002] IS27C020 [CX0001]  
IS27C020@PLCC32 [CX2032] IS27C020@TSOP32 [CX1002]  
IS27C256 [CX0001] IS27C256@PLCC32 [CX2032]  
IS27C512 [CX0001] IS27C512@PLCC32 [CX2032]  
IS27C512@TSOP28 [CX1024] IS27HC010 [CX0001]  
IS27HC010@PLCC32 [CX2032] IS27HC010@TSOP32 [CX1002]  
IS27HC020 [CX0001] IS27HC020@PLCC32 [CX2032]  
IS27HC020@TSOP32 [CX1002] IS27HC256 [CX0001]  
IS27HC256@PLCC32 [CX2032] IS27HC512 [CX0001]  
IS27HC512@PLCC32 [CX2032] IS27HC512@TSOP28 [CX1024]  
IS27LV010 [CX0001] IS27LV010@PLCC32 [CX2032]  
IS27LV010@TSOP32 [CX1002] IS27LV512 [CX0001]  
IS27LV512@PLCC32 [CX2032] IS27LV512@TSOP28 [CX1024]  
IS28F010 [CX0001] IS28F010@PLCC32 [CX2032]  
IS28F010@TSOP32 [CX1002] IS28F010A [CX0001]  
IS28F010A@PLCC32 [CX2032] IS28F010A@TSOP32 [CX1002]  
IS28F020 [CX0001] IS28F020@PLCC32 [CX2032]  
IS28F020@TSOP32 [CX1002] IS29F010 [CX0001]  
IS29F010@PLCC32 [CX2032] IS29F010@TSOP32 [CX1002]  
IS34C02 [CX0001] IS34C02@MSOP8 [CX1015]  
IS34C02@SOIC8 [CX1045] IS34C02@TSSOP8 [CX1059]  
IS34C02B@DFN8 IS34C02B@TSSOP8 [CX1059]  
IS71V08F32AS08@FBGA73 [CX5001] IS71V08F32BS08@FBGA73 [CX5001]  
IS71V08F32CS08@FBGA73 [CX5001] IS71V08F32DS08@FBGA73 [CX5001]  
IS71V08F32ES08@FBGA73 [CX5001] IS71V08F32ESB08@FBGA73 [CX5001]  
IS71V08F32EST08@FBGA73 [CX5001] IS71V08F32FS08@FBGA73 [CX5001]  
IS71V08F32GSB08@FBGA73 [CX5001] IS71V08F32GST08@FBGA73 [CX5001]  
IS71V08F64GS08@FBGA73 [CX5001] IS71V16F32AS08@FBGA73 [CX5001]  
IS71V16F32B04@FBGA56 [CX5045] IS71V16F32B04@FBGA59 [CX50UN]  
IS71V16F32BS08@FBGA73 [CX5001] IS71V16F32CS08@FBGA73 [CX5001]  
IS71V16F32DS08@FBGA73 [CX5001] IS71V16F32ES08@FBGA73 [CX5001]  
IS71V16F32ESB08@FBGA73 [CX5001] IS71V16F32EST08@FBGA73 [CX5001]  
IS71V16F32FS08@FBGA73 [CX5001] IS71V16F32GSB08@FBGA73 [CX5001]  
IS71V16F32GST08@FBGA73 [CX5001] IS71V16F32T04@FBGA56 [CX5045]



IS71V16F32T04@FBGA59 [CX50UN]	IS71V16F64GS08@FBGA73 [CX5001]
IS71VPCF32AS04@FBGA73 [CX5001]	IS71VPCF32BS04@FBGA73 [CX5001]
IS71VPCF32CS04@FBGA73 [CX5001]	IS71VPCF32DS04@FBGA73 [CX5001]
IS71VPCF32ES04@FBGA73 [CX5001]	IS71VPCF32FS04@FBGA73 [CX5001]
IS71VPCF64GS08@FBGA65 [CX5048]	IS75V16F64GS16@FBGA65 [CX5048]
IS75V16F64GS32@FBGA65 [CX5048]	IS93C46 [CX0001]
IS93C46@SOIC8 [CX1045]	IS93C46A(08bit) [CX0001]
IS93C46A(08bit)@SOIC8 [CX1045]	IS93C46A(08bit)@TSSOP8 [CX1059]
IS93C46A(16bit) [CX0001]	IS93C46A(16bit)@SOIC8 [CX1045]
IS93C46A(16bit)@TSSOP8 [CX1059]	IS93C46B [CX0001]
IS93C46B@SOIC8 [CX1045]	IS93C46B@TSSOP8 [CX1059]
IS93C46D(08bit) [CX0001]	IS93C46D(08bit)@SOIC8 [CX1045]
IS93C46D(08bit)@TSSOP8 [CX1059]	IS93C46D(16bit) [CX0001]
IS93C46D(16bit)@SOIC8 [CX1045]	IS93C46D(16bit)@TSSOP8 [CX1059]
IS93C56 [CX0001]	IS93C56@SOIC8 [CX1045]
IS93C56A(08bit) [CX0001]	IS93C56A(08bit)@SOIC8 [CX1045]
IS93C56A(08bit)@TSSOP8 [CX1059]	IS93C56A(16bit) [CX0001]
IS93C56A(16bit)@SOIC8 [CX1045]	IS93C56A(16bit)@TSSOP8 [CX1059]
IS93C66 [CX0001]	IS93C66@SOIC8 [CX1045]
IS93C66A(08bit) [CX0001]	IS93C66A(08bit)@SOIC8 [CX1045]
IS93C66A(08bit)@TSSOP8 [CX1059]	IS93C66A(16bit) [CX0001]
IS93C66A(16bit)@SOIC8 [CX1045]	IS93C66A(16bit)@TSSOP8 [CX1059]
IS93C76A(08bit) [CX0001]	IS93C76A(08bit)@SOIC8 [CX1045]
IS93C76A(08bit)@TSSOP8 [CX1059]	IS93C76A(16bit) [CX0001]
IS93C76A(16bit)@SOIC8 [CX1045]	IS93C76A(16bit)@TSSOP8 [CX1059]
IS93C86A(08bit) [CX0001]	IS93C86A(08bit)@SOIC8 [CX1045]
IS93C86A(08bit)@TSSOP8 [CX1059]	IS93C86A(16bit) [CX0001]
IS93C86A(16bit)@SOIC8 [CX1045]	IS93C86A(16bit)@TSSOP8 [CX1059]

#### DRAM & SRAM

IS61C1024 [CX0001]	IS61C1024(300m)@SOJ32 [CX1038]
IS61C1024(400m)@SOJ32 [CX1039]	IS61C1024@TSOP32 [CX1002]
IS61C1024L [CX0001]	IS61C1024L(300m)@SOJ32 [CX1038]
IS61C1024L(400m)@SOJ32 [CX1039]	IS61C1024L@TSOP32 [CX1002]
IS61C256AH [CX0001]	IS61C256AH@SOJ28
IS61C256AH@TSOP28 [CX1001]	IS61C512 [CX0001]
IS61C512(300m)@SOJ32 [CX1038]	IS61C512(400m)@SOJ32 [CX1039]
IS61C512@TSOP32 [CX1002]	IS61C64AH [CX0001]
IS61C64AH@SOJ28	IS61C64AH@TSOP28 [CX1001]
IS61LV256 [CX0001]	IS61LV256@SOJ28
IS61LV256@TSOP28 [CX1001]	IS61M256 [CX0001]
IS61M256@SOJ28	IS61M256@TSOP28 [CX1001]
IS62C1024 [CX0001]	IS62C1024(300m)@SOJ32 [CX1038]
IS62C1024(400m)@SOJ32 [CX1039]	IS62C1024@TSOP32 [CX1002]
IS62C256 [CX0001]	IS62C256@SOJ28
IS62C256@TSOP28 [CX1001]	IS62C512 [CX0001]
IS62C512(300m)@SOJ32 [CX1038]	IS62C512(400m)@SOJ32 [CX1039]
IS62C512@TSOP32 [CX1002]	IS62C64 [CX0001]
IS62C64@SOJ28	IS62C64@TSOP28 [CX1001]
IS62LV256 [CX0001]	IS62LV256@SOJ28
IS62LV256@TSOP28 [CX1001]	

#### MICROCONTROLLER

IS89C51A [CX0001]	IS89C51A@PLCC44 [CX2044]
IS89C51A@TQFP44 [CX3002]	IS89C52A [CX0001]
IS89C52A@PLCC44 [CX2044]	IS89C52A@TQFP44 [CX3002]

## K-LINE

### E (E) PROM/FRAM/NVRAM

K24C32 [CX0001]  
K24C32@TSSOP8 [CX1059]  
K24C64@SOIC8 [CX1045]

K24C32@SOIC8 [CX1045]  
K24C64 [CX0001]  
K24C64@TSSOP8 [CX1059]

## KODENSHI

### E (E) PROM/FRAM/NVRAM

KK24LC02B [CX0001]  
KK24LC04B [CX0001]  
KK24LC08B [CX0001]  
KK24LC16B [CX0001]

KK24LC02B@SOIC8 [CX1045]  
KK24LC04B@SOIC8 [CX1045]  
KK24LC08B@SOIC8 [CX1045]  
KK24LC16B@SOIC8 [CX1045]

## LATTICE

### PLD

GAL16LV8 [CX0001]  
GAL16LV8C [CX0001]  
GAL16LV8D [CX0001]  
GAL16LV8Z [CX0001]  
GAL16LV8ZD [CX0001]  
GAL16V8 [CX0001]  
GAL16V8@SOIC20 [CX1033]  
GAL16V8A@PLCC20 [CX2020]  
GAL16V8B [CX0001]  
GAL16V8B@SOIC20 [CX1033]  
GAL16V8C@PLCC20 [CX2020]  
GAL16V8D [CX0001]  
GAL16V8D@SOIC20 [CX1033]  
GAL16V8Z@PLCC20 [CX2020]  
GAL16VP8 [CX0001]  
GAL16VP8B [CX0001]  
GAL18V10 [CX0001]  
GAL18V10B [CX0001]  
GAL20LV8 [CX0001]  
GAL20LV8Z [CX0001]  
GAL20LV8ZD [CX0001]  
GAL20RA10 [CX0001]  
GAL20RA10B [CX0001]  
GAL20V8 [CX0001]  
GAL20V8A [CX0001]  
GAL20V8B [CX0001]  
GAL20V8C [CX0001]  
GAL20V8Z [CX0001]  
GAL20XV10 [CX0001]  
GAL20XV10B [CX0001]  
GAL22V10 [CX0001]  
GAL22V10@SOIC24 [CX1033]  
GAL22V10A@PLCC28 [CX2028]  
GAL22V10B [CX0001]

GAL16LV8@PLCC20 [CX2020]  
GAL16LV8C@PLCC20 [CX2020]  
GAL16LV8D@PLCC20 [CX2020]  
GAL16LV8Z@PLCC20 [CX2020]  
GAL16LV8ZD@PLCC20 [CX2020]  
GAL16V8@PLCC20 [CX2020]  
GAL16V8A [CX0001]  
GAL16V8A@SOIC20 [CX1033]  
GAL16V8B@PLCC20 [CX2020]  
GAL16V8C [CX0001]  
GAL16V8C@SOIC20 [CX1033]  
GAL16V8D@PLCC20 [CX2020]  
GAL16V8Z [CX0001]  
GAL16V8Z@SOIC20 [CX1033]  
GAL16VP8@PLCC20 [CX2020]  
GAL16VP8B@PLCC20 [CX2020]  
GAL18V10@PLCC20 [CX2020]  
GAL18V10B@PLCC20 [CX2020]  
GAL20LV8@PLCC28 [CX2028]  
GAL20LV8Z@PLCC28 [CX2028]  
GAL20LV8ZD@PLCC28 [CX2028]  
GAL20RA10@PLCC28 [CX2028]  
GAL20RA10B@PLCC28 [CX2028]  
GAL20V8@PLCC28 [CX2028]  
GAL20V8A@PLCC28 [CX2028]  
GAL20V8B@PLCC28 [CX2028]  
GAL20V8C@PLCC28 [CX2028]  
GAL20V8Z@PLCC28 [CX2028]  
GAL20XV10@PLCC28 [CX2028]  
GAL20XV10B@PLCC28 [CX2028]  
GAL22V10@PLCC28 [CX2028]  
GAL22V10A [CX0001]  
GAL22V10A@SOIC24 [CX1033]  
GAL22V10B@PLCC28 [CX2028]

GAL22V10B@SOIC24 [CX1033]  
GAL22V10BQ@PLCC28 [CX2028]  
GAL22V10C [CX0001]  
GAL22V10C@SOIC24 [CX1033]  
GAL22V10D@PLCC28 [CX2028]  
GAL26CLV12 [CX0001]  
GAL26CLV12@SOIC28 [CX1033]  
GAL26CLV12B [CX0001]  
GAL26CLV12B@SOIC28 [CX1033]  
GAL26CLV12C [CX0001]  
GAL26CLV12C@SOIC28 [CX1033]  
GAL26CLV12D [CX0001]  
GAL26CLV12D@SOIC28 [CX1033]  
GAL26CLV12Z [CX0001]  
GAL26CLV12Z@SOIC28 [CX1033]  
GAL26CLV12ZD [CX0001]  
GAL26CLV12ZD@SOIC28 [CX1033]  
GAL26CV12 [CX0001]  
GAL26CV12B [CX0001]  
GAL26CV12C [CX0001]  
GAL26V12C [CX0001]  
GAL6001B [CX0001]  
GAL6002B [CX0001]  
ispGAL22LV10 [CX0001]  
ispGAL22LV10@SSOP28 [CX1026]  
ispGAL22LV10A@PLCC28 [CX2028]  
ispGAL22LV10B [CX0001]  
ispGAL22LV10B@SSOP28 [CX1026]  
ispGAL22LV10C@PLCC28 [CX2028]  
ispGAL22LV10D [CX0001]  
ispGAL22LV10D@SSOP28 [CX1026]  
ispGAL22V10AB@QFN32 [CX4015]  
ispGAL22V10AC@QFN32 [CX4015]  
ispGAL22V10AV@QFN32 [CX4015]  
ispGAL22V10AZC@QFN32 [CX4015]  
ispGAL22V10C(UES)@PLCC28 [CX2028]  
ispGAL22V10C(UES)@SSOP28 [CX1026]  
ispGAL22V10C@PLCC28 [CX2028]  
ispGDX80VA@TQFP100 [CX3021]  
ispLSI1016@TQFP44 [CX3003]  
ispLSI1016E@TQFP44 [CX3003]  
ispLSI1024E@PLCC68 [CX2068]  
ispLSI1032@PLCC84 [CX2084]  
ispLSI1032E@CPGA84 [CX5000]  
ispLSI1032E@TQFP100 [CX3021]  
ispLSI2032@TQFP44 [CX3003]  
ispLSI2032A@TQFP44 [CX3003]  
ispLSI2064@CPGA84 [CX5000]  
ispLSI2064@TQFP100 [CX3021]  
ispLSI2064A@PLCC84 [CX2084]  
ispLSI2064A@TQFP44 [CX3003]  
ispLSI2096E@TQFP128(ISP) [CX3030]  
ispLSI2096VE@TQFP128(ISP) [CX3030]  
ispLSI2128A@PLCC84 [CX2084]  
LC4032B@TQFP44 [CX3003]  
LC4032C@TQFP44 [CX3003]  
LC4032V@TQFP44 [CX3003]  
LC4032ZC@TQFP48 [CX3007]  
LC4064V@TQFP44 [CX3003]

GAL22V10BQ [CX0001]  
GAL22V10BQ@SOIC24 [CX1033]  
GAL22V10C@PLCC28 [CX2028]  
GAL22V10D [CX0001]  
GAL22V10D@SOIC24 [CX1033]  
GAL26CLV12@PLCC28 [CX2028]  
GAL26CLV12@TSOP28 [CX1001]  
GAL26CLV12B@PLCC28 [CX2028]  
GAL26CLV12B@TSOP28 [CX1001]  
GAL26CLV12C@PLCC28 [CX2028]  
GAL26CLV12C@TSOP28 [CX1001]  
GAL26CLV12D@PLCC28 [CX2028]  
GAL26CLV12D@TSOP28 [CX1001]  
GAL26CLV12Z@PLCC28 [CX2028]  
GAL26CLV12Z@TSOP28 [CX1001]  
GAL26CLV12ZD@PLCC28 [CX2028]  
GAL26CLV12ZD@TSOP28 [CX1001]  
GAL26CV12@PLCC28 [CX2028]  
GAL26CV12B@PLCC28 [CX2028]  
GAL26CV12C@PLCC28 [CX2028]  
GAL26V12C@PLCC28 [CX2028]  
GAL6001B@PLCC28 [CX2028]  
GAL6002B@PLCC28 [CX2028]  
ispGAL22LV10@PLCC28 [CX2028]  
ispGAL22LV10A [CX0001]  
ispGAL22LV10A@SSOP28 [CX1026]  
ispGAL22LV10B@PLCC28 [CX2028]  
ispGAL22LV10C [CX0001]  
ispGAL22LV10C@SSOP28 [CX1026]  
ispGAL22LV10D@PLCC28 [CX2028]  
ispGAL22V10AB@PLCC28 [CX2028]  
ispGAL22V10AC@PLCC28 [CX2028]  
ispGAL22V10AV@PLCC28 [CX2028]  
ispGAL22V10AZC@PLCC28 [CX2028]  
  
ispGAL22V10C@SSOP28 [CX1026]  
ispLSI1016@PLCC44 [CX2044]  
ispLSI1016E@PLCC44 [CX2044]  
ispLSI1024@PLCC68 [CX2068]  
ispLSI1032@CPGA84 [CX5000]  
ispLSI1032@TQFP100 [CX3021]  
ispLSI1032E@PLCC84 [CX2084]  
ispLSI2032@PLCC44 [CX2044]  
ispLSI2032A@PLCC44 [CX2044]  
ispLSI2032A@TQFP48 [CX3007]  
ispLSI2064@PLCC84 [CX2084]  
ispLSI2064A@PLCC44 [CX2044]  
ispLSI2064A@TQFP100 [CX3021]  
  
ispLSI2128A@TQFP100 [CX3021]  
LC4032B@TQFP48 [CX3007]  
LC4032C@TQFP48 [CX3007]  
LC4032V@TQFP48 [CX3007]  
LC4032ZE@TQFP48 [CX3007]  
LC4064V@TQFP48 [CX3007]

LCMXO1200C_3T100 [CX3021]	LCMXO1200C_4T100 [CX3021]
LCMXO1200C_5T100 [CX3021]	LCMXO1200E_3T100 [CX3021]
LCMXO1200E_4T100 [CX3021]	LCMXO1200E_5T100 [CX3021]
LCMXO2280C_3T100 [CX3021]	LCMXO2280C_4T100 [CX3021]
LCMXO2280C_5T100 [CX3021]	LCMXO2280E_3T100 [CX3021]
LCMXO2280E_4T100 [CX3021]	LCMXO2280E_5T100 [CX3021]
LCMXO256C-3T100 [CX3021]	LCMXO256C-4T100 [CX3021]
LCMXO256C-5T100 [CX3021]	LCMXO256E-3T100 [CX3021]
LCMXO256E-4T100 [CX3021]	LCMXO256E-5T100 [CX3021]
LCMXO640C_3T100 [CX3021]	LCMXO640C_4T100 [CX3021]
LCMXO640C_5T100 [CX3021]	LCMXO640E_3T100 [CX3021]
LCMXO640E_4T100 [CX3021]	LCMXO640E_5T100 [CX3021]
M4-128/64@PQFP100 [CX3022]	M4-128/64@TQFP100 [CX3021]
M4-128N/64@PLCC84 [CX2084]	M4LV-128/64@PQFP100 [CX3022]
M4LV-128/64@TQFP100 [CX3021]	M4LV-128N/64@PLCC84 [CX2084]
M4LV-64/32@PLCC44 [CX2044]	M4LV-64/32@TQFP44 [CX3003]
M4LV-64/32@TQFP48 [CX3007]	MACH110@PLCC44 [CX2044]
MACH111@PLCC44 [CX2044]	MACH111@TQFP44 [CX3003]
MACH130@PLCC84 [CX2084]	MACH131/1@PLCC84 [CX2084]
MACH131@PLCC84 [CX2084]	MACH131SP@PQFP100 [CX3022]
MACH131SP@TQFP100 [CX3021]	MACH210@PLCC44 [CX2044]
MACH210@TQFP44 [CX3003]	MACH210A@PLCC44 [CX2044]
MACH210A@TQFP44 [CX3003]	MACH210AQ@PLCC44 [CX2044]
MACH210AQ@TQFP44 [CX3003]	MACH211@PLCC44 [CX2044]
MACH220@PLCC68 [CX2068]	MACH221@PLCC68 [CX2068]
MACH231SP@PLCC84 [CX2084]	MACH231SP@PQFP100 [CX3022]
MACH231SP@TQFP100 [CX3021]	MACH435@PLCC84 [CX2084]
MACH436@PLCC84 [CX2084]	MACH446@PQFP100 [CX3022]
MACH446@TQFP100 [CX3021]	MACHLV210@PLCC44 [CX2044]
MACHLV210@TQFP44 [CX3003]	MACHLV436@PLCC84 [CX2084]
MACHLV446@PQFP100 [CX3022]	MACHLV446@TQFP100 [CX3021]
PAL29M16H [CX0001]	PALCE20RA10 [CX0001]
PALCE20RA10@PLCC28 [CX2028]	PALCE20RA10@SOIC24 [CX1033]
PALCE20RA10H [CX0001]	PALCE20RA10H@PLCC28 [CX2028]
PALCE20RA10H@SOIC24 [CX1033]	PALCE20RA10Q [CX0001]
PALCE20RA10Q@PLCC28 [CX2028]	PALCE20RA10Q@SOIC24 [CX1033]
PALCE22V10H [CX0001]	PALCE22V10H@PLCC28 [CX2028]
PALCE22V10H@SOIC24 [CX1003]	PALCE22V10Q [CX0001]
PALCE22V10Q@PLCC28 [CX2028]	PALCE22V10Q@SOIC24 [CX1003]
PALCE22V10Z [CX0001]	PALCE22V10Z@PLCC28 [CX2028]
PALCE22V10Z@SOIC24 [CX1003]	PALCE26V12H/4 [CX0001]
PALCE26V12H/4@PLCC28 [CX2028]	PALCE26V12H/4@SOIC28 [CX1033]
PALCE26V12H-15 [CX0001]	PALCE26V12H-15@PLCC28 [CX0001]
PALCE26V12H-15@SOIC28 [CX0001]	PALCE26V12H-20 [CX0001]
PALCE26V12H-20@PLCC28 [CX0001]	PALCE26V12H-20@SOIC28 [CX0001]
PALCE26V12H-25 [CX0001]	PALCE26V12H-25@PLCC28 [CX0001]
PALCE26V12H-25@SOIC28 [CX0001]	PALCE29M16H [CX0001]
PALCE29M16H@PLCC28 [CX2028]	PALCE29M16H@SOIC24 [CX1033]
PALCE29MA16H [CX0001]	PALCE29MA16H@PLCC28 [CX2028]
PALCE29MA16H@SOIC24 [CX1033]	PALCE610 [CX0001]
PALCE610@PLCC28 [CX2028]	PALCE610@SOIC24 [CX1003]
PALCE610H [CX0001]	PALCE610H@PLCC28 [CX2028]
PALCE610H@SOIC24 [CX1003]	PALCE630H [CX0001]
PALCE630H@PLCC28 [CX2028]	PALCE630H@SOIC24 [CX1003]

## LG Semicon

GM76C256CL [CX0001]  
GM76C256CL@TSOP28 [CX1001]  
GM76C256CLL@SSOP28 [CX1063]  
GM76C8128CL [CX0001]  
GM76C8128CL@TSOP32 [CX1002]  
GM76C8128CLL [CX0001]  
GM76C8128CLL@TSOP32 [CX1002]  
GM76C88AL [CX0001]  
GM76C88AL@TSOP28 [CX1001]  
GM76U256CL@SSOP28  
GM76U256CLL [CX0001]  
GM76U256CLL@TSOP28 [CX1001]  
GM76U8128CL@SSOP32 [CX1019]  
GM76U8128CL@VSOP32 [CX1003]  
GM76U8128CLL@SSOP32 [CX1019]  
GM76U8128CLL@VSOP32 [CX1003]  
GM76U8128DL@SSOP32 [CX1019]  
GM76U8128DL@VSOP32 [CX1003]  
GM76U8128DLL@SSOP32 [CX1019]  
GM76U8128DLL@VSOP32 [CX1003]  
GM76U8512L@SSOP32  
GM76U8512L@VSOP32 [CX1003]  
GM76U8512LL@SSOP32 [CX1019]  
GM76U8512LL@VSOP32 [CX1003]  
GM76V256CL@SSOP28  
GM76V256CLL [CX0001]  
GM76V256CLL@TSOP28 [CX1001]  
GM76V8128CL@SSOP32 [CX1019]  
GM76V8128CL@VSOP32 [CX1003]  
GM76V8128CLL@SSOP32 [CX1019]  
GM76V8128CLL@VSOP32 [CX1003]  
GM76V8128DL@SSOP32 [CX1019]  
GM76V8128DL@VSOP32 [CX1003]  
GM76V8128DLL@SSOP32 [CX1019]  
GM76V8128DLL@VSOP32 [CX1003]  
GM76V8512L@SSOP32 [CX1019]  
GM76V8512L@VSOP32 [CX1003]  
GM76V8512LL@SSOP32 [CX1019]  
GM76V8512LL@VSOP32 [CX1003]  
GM77C8128A@SSOP32 [CX1019]  
GM77C8128A@VSOP32 [CX1003]

GM76C256CL@SSOP28 [CX1063]  
GM76C256CLL [CX0001]  
GM76C256CLL@TSOP28 [CX1001]  
GM76C8128CL@SSOP32 [CX1019]  
GM76C8128CL@VSOP32 [CX1003]  
GM76C8128CLL@SSOP32 [CX1019]  
GM76C8128CLL@VSOP32 [CX1003]  
GM76C88AL@SSOP28  
GM76U256CL [CX0001]  
GM76U256CL@TSOP28 [CX1001]  
GM76U256CLL@SSOP28  
GM76U8128CL [CX0001]  
GM76U8128CL@TSOP32 [CX1002]  
GM76U8128CLL [CX0001]  
GM76U8128CLL@TSOP32 [CX1002]  
GM76U8128DL [CX0001]  
GM76U8128DL@TSOP32 [CX1002]  
GM76U8128DLL [CX0001]  
GM76U8128DLL@TSOP32 [CX1002]  
GM76U8512L [CX0001]  
GM76U8512L@TSOP32 [CX1002]  
GM76U8512LL [CX0001]  
GM76U8512LL@TSOP32 [CX1002]  
GM76V256CL [CX0001]  
GM76V256CL@TSOP28 [CX1001]  
GM76V256CLL@SSOP28  
GM76V8128CL [CX0001]  
GM76V8128CL@TSOP32 [CX1002]  
GM76V8128CLL [CX0001]  
GM76V8128CLL@TSOP32 [CX1002]  
GM76V8128DL [CX0001]  
GM76V8128DL@TSOP32 [CX1002]  
GM76V8128DLL [CX0001]  
GM76V8128DLL@TSOP32 [CX1002]  
GM76V8512L [CX0001]  
GM76V8512L@TSOP32 [CX1002]  
GM76V8512LL [CX0001]  
GM76V8512LL@TSOP32 [CX1002]  
GM77C8128A [CX0001]  
GM77C8128A@TSOP32 [CX1002]

## MICROCONTROLLER

GMS34004TK [CX0001]  
GMS34004TW [CX0001]  
GMS34112TK@SOIC20 [CX1033]  
GMS34140TK [CX0001]  
GMS80C701 [CX0001]  
GMS80C701@TQFP44 [CX3002]  
GMS81004(dip24) [CX0001]  
GMS81004@PLCC44 [CX2044]  
GMS81004@SOIC24 [CX1033]  
GMS81008(dip20) [CX0001]  
GMS81008(dip28) [CX0001]  
GMS81008@SOIC20 [CX1033]  
GMS81008@SOIC28 [CX1033]  
GMS81016(dip24) [CX0001]

GMS34004TM [CX0001]  
GMS34112TK [CX0001]  
GMS34112TK@SSOP20 [CX1026]  
GMS34140TK@SOIC24 [CX1033]  
GMS80C701@PLCC44 [CX2044]  
GMS81004(dip20) [CX0001]  
GMS81004(dip28) [CX0001]  
GMS81004@SOIC20 [CX1033]  
GMS81004@SOIC28 [CX1033]  
GMS81008(dip24) [CX0001]  
GMS81008@PLCC44 [CX2044]  
GMS81008@SOIC24 [CX1033]  
GMS81016(dip20) [CX0001]  
GMS81016(dip28) [CX0001]

GMS81016@PLCC44 [CX2044]  
GMS81016@SOIC24 [CX1033]  
GMS81024(dip20) [CX0001]  
GMS81024(dip28) [CX0001]  
GMS81024@SOIC20 [CX1033]  
GMS81024@SOIC28 [CX1033]  
GMS81032(dip24) [CX0001]  
GMS81032@PLCC44 [CX2044]  
GMS81032@SOIC24 [CX1033]  
GMS81504AT [CX0032]  
GMS81516 [CX0001]  
GMS81516BT [CX0001]  
GMS81524AT [CX0001]  
GMS81604T [CX0001]  
GMS81604T@SDIP42 [CX0042]  
GMS81608T@PLCC44 [CX2044]  
GMS81C5016(dip28) [CX0001]  
GMS81C5016@PLCC44 [CX2044]  
GMS81C5016@TQFP44 [CX3002]  
GMS81C5024(dip40) [CX0001]  
GMS81C5024@SOIC28 [CX1033]  
GMS81C5032(dip28) [CX0001]  
GMS81C5032@PLCC44 [CX2044]  
GMS81C5032@TQFP44 [CX3002]  
GMS82516T@MQFP44 [CX3002]  
GMS82524T [CX0001]  
GMS82524T@SDIP42 [CX0042]  
GMS87C1102@SOP16 [CX1033]  
GMS87C1202@SOP20 [CX1033]  
GMS87C1404@SOP28 [CX1033]  
GMS87C1408@SOP28 [CX1033]  
GMS87C5032(dip40) [CX0001]  
GMS87C5032@SOIC28 [CX1033]  
GMS97C1051 [CX0001]  
GMS97C2051 [CX0001]  
GMS97C51 [CX0001]  
GMS97C51@TQFP44 [CX3002]  
GMS97C52@PLCC44 [CX2044]  
GMS97C54 [CX0001]  
GMS97C54@TQFP44 [CX3002]  
GMS97C56@PLCC44 [CX2044]  
GMS97C58 [CX0001]  
GMS97C58@TQFP44 [CX3002]  
GMS97L1051@SOIC20 [CX1033]  
GMS97L2051@SOIC20 [CX1033]  
GMS97L51@PLCC44 [CX2044]  
GMS97L52 [CX0001]  
GMS97L52@TQFP44 [CX3002]  
GMS97L54@PLCC44 [CX2044]  
GMS97L56 [CX0001]  
GMS97L56@TQFP44 [CX3002]  
GMS97L58@PLCC44 [CX2044]  
GMS99C51 [CX0001]  
GMS99C51@TQFP44 [CX3002]  
GMS99C52@PLCC44 [CX2044]  
GMS99C58 [CX0001]  
GMS99C58@TQFP44 [CX3002]  
GMS81016@SOIC20 [CX1033]  
GMS81016@SOIC28 [CX1033]  
GMS81024(dip24) [CX0001]  
GMS81024@PLCC44 [CX2044]  
GMS81024@SOIC24 [CX1033]  
GMS81032(dip20) [CX0001]  
GMS81032(dip28) [CX0001]  
GMS81032@SOIC20 [CX1033]  
GMS81032@SOIC28 [CX1033]  
GMS81504T [CX0032]  
GMS81516AT [CX0001]  
GMS81524 [CX0001]  
GMS81524BT [CX0001]  
GMS81604T@PLCC44 [CX2044]  
GMS81608T [CX0001]  
GMS81608T@SDIP42 [CX0042]  
GMS81C5016(dip40) [CX0001]  
GMS81C5016@SOIC28 [CX1033]  
GMS81C5024(dip28) [CX0001]  
GMS81C5024@PLCC44 [CX2044]  
GMS81C5024@TQFP44 [CX3002]  
GMS81C5032(dip40) [CX0001]  
GMS81C5032@SOIC28 [CX1033]  
GMS82516T [CX0001]  
GMS82516T@SDIP42 [CX0042]  
GMS82524T@MQFP44 [CX3002]  
GMS87C1102 [CX0001]  
GMS87C1202 [CX0001]  
GMS87C1404 [CX0001]  
GMS87C1408 [CX0001]  
GMS87C5032(dip28) [CX0001]  
GMS87C5032@PLCC44 [CX2044]  
GMS87C5032@TQFP44 [CX3002]  
GMS97C1051@SOIC20 [CX1033]  
GMS97C2051@SOIC20 [CX1033]  
GMS97C51@PLCC44 [CX2044]  
GMS97C52 [CX0001]  
GMS97C52@TQFP44 [CX3002]  
GMS97C54@PLCC44 [CX2044]  
GMS97C56 [CX0001]  
GMS97C56@TQFP44 [CX3002]  
GMS97C58@PLCC44 [CX2044]  
GMS97L1051 [CX0001]  
GMS97L2051 [CX0001]  
GMS97L51 [CX0001]  
GMS97L51@TQFP44 [CX3002]  
GMS97L52@PLCC44 [CX2044]  
GMS97L54 [CX0001]  
GMS97L54@TQFP44 [CX3002]  
GMS97L56@PLCC44 [CX2044]  
GMS97L58 [CX0001]  
GMS97L58@TQFP44 [CX3002]  
GMS99C51@PLCC44 [CX2044]  
GMS99C52 [CX0001]  
GMS99C52@TQFP44 [CX3002]  
GMS99C58@PLCC44 [CX2044]

## LINEAR

### MICROCONTROLLER

LTC2978@QFN64 [CX4023]

LTC3880@QFN64 [CX4023]

## LINKSMART

### E (E) PROM/FRAM/NVRAM

L24C02 [CX0001]

L24C02@TSOP8 [CX1059]

L24C04@SSOP8 [CX1045]

L29004C [CX0001]

L29004C@TSOP32 [CX1002]

L29S160F-B@TSOP48 [CX1004]

L29S400F@TSOP48 [CX1004]

L29S400F-B@TSOP48 [CX1004]

L29S800F-B@TSOP48 [CX1004]

L29W800E-B@TSOP48 [CX1004]

LST28001@PLCC32 [CX2032]

LST28002 [CX0001]

LST28002@TSOP32 [CX1002]

LST28004@PLCC32 [CX2032]

L24C02@SSOP8 [CX1045]

L24C04 [CX0001]

L24C04@TSOP8 [CX1059]

L29004C@PLCC32 [CX2032]

L29S160F@TSOP48 [CX1004]

L29S400F@PSOP44 [CX1014]

L29S400F-B@PSOP44 [CX1014]

L29S800F@TSOP48 [CX1004]

L29W800E@TSOP48 [CX1004]

LST28001 [CX0001]

LST28001@TSOP32 [CX1002]

LST28002@PLCC32 [CX2032]

LST28004 [CX0001]

LST28004@TSOP32 [CX1002]

## LITAO

### E (E) PROM/FRAM/NVRAM

L24C01 [CX0001]

L24C04 [CX0001]

L24C16 [CX0001]

L24C02 [CX0001]

L24C08 [CX0001]

## LIZE

### E (E) PROM/FRAM/NVRAM

L24C02 [CX0001]

L24C02@TSSOP8 [CX1059]

L24C04@SOP8 [CX1045]

L24C08 [CX0001]

L24C08@TSSOP8 [CX1059]

L24C16@SOP8 [CX1045]

L24C02@SOP8 [CX1045]

L24C04 [CX0001]

L24C04@TSSOP8 [CX1059]

L24C08@SOP8 [CX1045]

L24C16 [CX0001]

L24C16@TSSOP8 [CX1059]

## LUMINARY

### MICROCONTROLLER

LM3S101(new)@SOIC28 [CX1033]

LM3S101(new)@SOIC28(ISP) [CX0001]

LM3S101(old)@SOIC28 [CX1033]

LM3S101(old)@SOIC28(ISP) [CX0001]

LM3S102(new)@SOIC28 [CX1033]

LM3S102(new)@SOIC28(ISP) [CX0001]

LM3S102(old)@SOIC28 [CX1033]

LM3S102(old)@SOIC28(ISP) [CX0001]  
LM3S1110@BGA108(ISP) [CX0001]  
LM3S1110@TQFP100(ISP) [CX0001]  
LM3S1133@TQFP100 [CX3021]  
LM3S1138@BGA108(ISP) [CX0001]  
LM3S1138@TQFP100(ISP) [CX0001]  
LM3S1150@TQFP100 [CX3021]  
LM3S1162@BGA108(ISP) [CX0001]  
LM3S1162@TQFP100(ISP) [CX0001]  
LM3S1165@TQFP100 [CX3021]  
LM3S1332@BGA108(ISP) [CX0001]  
LM3S1332@TQFP100(ISP) [CX0001]  
LM3S1435@TQFP100 [CX3021]  
LM3S1439@BGA108(ISP) [CX0001]  
LM3S1439@TQFP100(ISP) [CX0001]  
LM3S1512@TQFP100 [CX3021]  
LM3S1538@BGA108(ISP) [CX0001]  
LM3S1538@TQFP100(ISP) [CX0001]  
LM3S1601@TQFP100 [CX3021]  
LM3S1607@TQFP64 [CX3011]  
LM3S1608@BGA108(ISP) [CX0001]  
LM3S1608@TQFP100(ISP) [CX0001]  
LM3S1620@TQFP100 [CX3021]  
LM3S1625@TQFP64 [CX3011]  
LM3S1626@TQFP64 [CX3011]  
LM3S1627@TQFP64 [CX3011]  
LM3S1635@BGA108(ISP) [CX0001]  
LM3S1635@TQFP100(ISP) [CX0001]  
LM3S1637@TQFP100 [CX3021]  
LM3S1751@BGA108(ISP) [CX0001]  
LM3S1751@TQFP100(ISP) [CX0001]  
LM3S1776@TQFP64(ISP) [CX0001]  
LM3S1850@TQFP100 [CX3021]  
LM3S1911@BGA108(ISP) [CX0001]  
LM3S1911@TQFP100(ISP) [CX0001]  
LM3S1918@TQFP100 [CX3021]  
LM3S1937@BGA108(ISP) [CX0001]  
LM3S1937@TQFP100(ISP) [CX0001]  
LM3S1958@TQFP100 [CX3021]  
LM3S1960@BGA108(ISP) [CX0001]  
LM3S1960@TQFP100(ISP) [CX0001]  
LM3S1968@TQFP100 [CX3021]  
LM3S2016@BGA108(ISP) [CX0001]  
LM3S2016@TQFP100(ISP) [CX0001]  
LM3S2110@TQFP100 [CX3021]  
LM3S2139@BGA108(ISP) [CX0001]  
LM3S2139@TQFP100(ISP) [CX0001]  
LM3S2276@TQFP64(ISP) [CX0001]  
LM3S2410@TQFP100 [CX3021]  
LM3S2412@BGA108(ISP) [CX0001]  
LM3S2412@TQFP100(ISP) [CX0001]  
LM3S2432@TQFP100 [CX3021]  
LM3S2533@BGA108(ISP) [CX0001]  
LM3S2533@TQFP100(ISP) [CX0001]  
LM3S2601@TQFP100 [CX3021]  
LM3S2608@BGA108(ISP) [CX0001]  
LM3S2608@TQFP100(ISP) [CX0001]  
LM3S2616@TQFP64(ISP) [CX0001]  
LM3S2620@TQFP100 [CX3021]  
LM3S1110@TQFP100 [CX3021]  
LM3S1133@BGA108(ISP) [CX0001]  
LM3S1133@TQFP100(ISP) [CX0001]  
LM3S1138@TQFP100 [CX3021]  
LM3S1150@BGA108(ISP) [CX0001]  
LM3S1150@TQFP100(ISP) [CX0001]  
LM3S1162@TQFP100 [CX3021]  
LM3S1165@BGA108(ISP) [CX0001]  
LM3S1165@TQFP100(ISP) [CX0001]  
LM3S1332@TQFP100 [CX3021]  
LM3S1435@BGA108(ISP) [CX0001]  
LM3S1435@TQFP100(ISP) [CX0001]  
LM3S1439@TQFP100 [CX3021]  
LM3S1512@BGA108(ISP) [CX0001]  
LM3S1512@TQFP100(ISP) [CX0001]  
LM3S1538@TQFP100 [CX3021]  
LM3S1601@BGA108(ISP) [CX0001]  
LM3S1601@TQFP100(ISP) [CX0001]  
LM3S1607@TQFP64(ISP) [CX0001]  
LM3S1608@TQFP100 [CX3021]  
LM3S1620@BGA108(ISP) [CX0001]  
LM3S1620@TQFP100(ISP) [CX0001]  
LM3S1625@TQFP64(ISP) [CX0001]  
LM3S1626@TQFP64(ISP) [CX0001]  
LM3S1627@TQFP64(ISP) [CX0001]  
LM3S1635@TQFP100 [CX3021]  
LM3S1637@BGA108(ISP) [CX0001]  
LM3S1637@TQFP100(ISP) [CX0001]  
LM3S1751@TQFP100 [CX3021]  
LM3S1776@TQFP64 [CX3011]  
LM3S1850@BGA108(ISP) [CX0001]  
LM3S1850@TQFP100(ISP) [CX0001]  
LM3S1911@TQFP100 [CX3021]  
LM3S1918@BGA108(ISP) [CX0001]  
LM3S1918@TQFP100(ISP) [CX0001]  
LM3S1937@TQFP100 [CX3021]  
LM3S1958@BGA108(ISP) [CX0001]  
LM3S1958@TQFP100(ISP) [CX0001]  
LM3S1960@TQFP100 [CX3021]  
LM3S1968@BGA108(ISP) [CX0001]  
LM3S1968@TQFP100(ISP) [CX0001]  
LM3S2016@TQFP100 [CX3021]  
LM3S2110@BGA108(ISP) [CX0001]  
LM3S2110@TQFP100(ISP) [CX0001]  
LM3S2139@TQFP100 [CX3021]  
LM3S2276@TQFP64 [CX3011]  
LM3S2410@BGA108(ISP) [CX0001]  
LM3S2410@TQFP100(ISP) [CX0001]  
LM3S2412@TQFP100 [CX3021]  
LM3S2432@BGA108(ISP) [CX0001]  
LM3S2432@TQFP100(ISP) [CX0001]  
LM3S2533@TQFP100 [CX3021]  
LM3S2601@BGA108(ISP) [CX0001]  
LM3S2601@TQFP100(ISP) [CX0001]  
LM3S2608@TQFP100 [CX3021]  
LM3S2616@TQFP64 [CX3011]  
LM3S2620@BGA108(ISP) [CX0001]  
LM3S2620@TQFP100(ISP) [CX0001]



LM3S2637@BGA108(ISP) [CX0001]  
LM3S2637@TQFP100(ISP) [CX0001]  
LM3S2651@TQFP100 [CX3021]  
LM3S2671@TQFP64 [CX3011]  
LM3S2678@TQFP64 [CX3011]  
LM3S2730@BGA108(ISP) [CX0001]  
LM3S2730@TQFP100(ISP) [CX0001]  
LM3S2739@TQFP100 [CX3021]  
LM3S2776@TQFP64 [CX3011]  
LM3S2911@BGA108(ISP) [CX0001]  
LM3S2911@TQFP100(ISP) [CX0001]  
LM3S2918@TQFP100 [CX3021]  
LM3S2939@BGA108(ISP) [CX0001]  
LM3S2939@TQFP100(ISP) [CX0001]  
LM3S2948@TQFP100 [CX3021]  
LM3S2950@BGA108(ISP) [CX0001]  
LM3S2950@TQFP100(ISP) [CX0001]  
LM3S2965@TQFP100 [CX3021]  
LM3S300@LQFP48 [CX3007]  
LM3S301(new)@LQFP48 [CX3007]  
LM3S301(new)@LQFP48(ISP) [CX0001]  
LM3S301(old)@LQFP48 [CX3007]  
LM3S301(old)@LQFP48(ISP) [CX0001]  
LM3S308@LQFP48 [CX3007]  
LM3S310(new)@LQFP48 [CX3007]  
LM3S310(new)@LQFP48(ISP) [CX0001]  
LM3S310(old)@LQFP48 [CX3007]  
LM3S310(old)@LQFP48(ISP) [CX0001]  
LM3S315(new)@LQFP48 [CX3007]  
LM3S315(new)@LQFP48(ISP) [CX0001]  
LM3S315(old)@LQFP48 [CX3007]  
LM3S315(old)@LQFP48(ISP) [CX0001]  
LM3S316(new)@LQFP48 [CX3007]  
LM3S316(new)@LQFP48(ISP) [CX0001]  
LM3S316(old)@LQFP48 [CX3007]  
LM3S316(old)@LQFP48(ISP) [CX0001]  
LM3S317(new)@LQFP48 [CX3007]  
LM3S317(new)@LQFP48(ISP) [CX0001]  
LM3S317(old)@LQFP48 [CX3007]  
LM3S317(old)@LQFP48(ISP) [CX0001]  
LM3S328(new)@LQFP48 [CX3007]  
LM3S328(new)@LQFP48(ISP) [CX0001]  
LM3S328(old)@LQFP48 [CX3007]  
LM3S328(old)@LQFP48(ISP) [CX0001]  
LM3S3651@TQFP64 [CX3011]  
LM3S3739@BGA108(ISP) [CX0001]  
LM3S3739@TQFP100(ISP) [CX0001]  
LM3S3748@TQFP100 [CX3021]  
LM3S3749@BGA108(ISP) [CX0001]  
LM3S3749@TQFP100(ISP) [CX0001]  
LM3S3759@TQFP100 [CX3021]  
LM3S3768@BGA108(ISP) [CX0001]  
LM3S3768@TQFP100(ISP) [CX0001]  
LM3S5632@TQFP64(ISP) [CX0001]  
LM3S5652@TQFP64(ISP) [CX0001]  
LM3S5662@TQFP64(ISP) [CX0001]  
LM3S5732@TQFP64(ISP) [CX0001]  
LM3S5737@TQFP100 [CX3021]  
LM3S5739@BGA108(ISP) [CX0001]  
LM3S2637@TQFP100 [CX3021]  
LM3S2651@BGA108(ISP) [CX0001]  
LM3S2651@TQFP100(ISP) [CX0001]  
LM3S2671@TQFP64(ISP) [CX0001]  
LM3S2678@TQFP64(ISP) [CX0001]  
LM3S2730@TQFP100 [CX3021]  
LM3S2739@BGA108(ISP) [CX0001]  
LM3S2739@TQFP100(ISP) [CX0001]  
LM3S2776@TQFP64(ISP) [CX0001]  
LM3S2911@TQFP100 [CX3021]  
LM3S2918@BGA108(ISP) [CX0001]  
LM3S2918@TQFP100(ISP) [CX0001]  
LM3S2939@TQFP100 [CX3021]  
LM3S2948@BGA108(ISP) [CX0001]  
LM3S2948@TQFP100(ISP) [CX0001]  
LM3S2950@TQFP100 [CX3021]  
LM3S2965@BGA108(ISP) [CX0001]  
LM3S2965@TQFP100(ISP) [CX0001]  
LM3S300@LQFP48(ISP) [CX0001]  
LM3S308@LQFP48(ISP) [CX0001]

LM3S5739@TQFP100(ISP) [CX0001] LM3S5747@BGA108(ISP) [CX0001]  
LM3S5747@TQFP100 [CX3021] LM3S5747@TQFP100(ISP) [CX0001]  
LM3S5749@BGA108(ISP) [CX0001] LM3S5749@TQFP100 [CX3021]  
LM3S5749@TQFP100(ISP) [CX0001] LM3S5752@TQFP64 [CX3011]  
LM3S5752@TQFP64(ISP) [CX0001] LM3S5757@BGA108(ISP) [CX0001]  
LM3S5757@TQFP100 [CX3021] LM3S5757@TQFP100(ISP) [CX0001]  
LM3S5762@TQFP64 [CX3011] LM3S5762@TQFP64(ISP) [CX0001]  
LM3S5767@BGA108(ISP) [CX0001] LM3S5767@TQFP100 [CX3021]  
LM3S5767@TQFP100(ISP) [CX0001] LM3S5768@BGA108(ISP) [CX0001]  
LM3S5768@TQFP100 [CX3021] LM3S5768@TQFP100(ISP) [CX0001]  
LM3S5769@BGA108(ISP) [CX0001] LM3S5769@TQFP100 [CX3021]  
LM3S5769@TQFP100(ISP) [CX0001] LM3S600@LQFP48 [CX3007]  
LM3S600@LQFP48(ISP) [CX0001] LM3S601(new)@LQFP48 [CX3007]  
LM3S601(new)@LQFP48(ISP) [CX0001] LM3S601(old)@LQFP48 [CX3007]  
LM3S601(old)@LQFP48(ISP) [CX0001] LM3S608@LQFP48(ISP) [CX0001]  
LM3S608@LQFP48 [CX3007] LM3S610(new)@LQFP48 [CX3007]  
LM3S610(new)@LQFP48(ISP) [CX0001] LM3S610(old)@LQFP48 [CX3007]  
LM3S610(old)@LQFP48(ISP) [CX0001] LM3S6100@BGA108(ISP) [CX0001]  
LM3S6100@TQFP100(ISP) [CX0001] LM3S611(new)@LQFP48(ISP) [CX0001]  
LM3S611(old)@LQFP48 [CX3007] LM3S611(old)@LQFP48(ISP) [CX0001]  
LM3S6110@BGA108(ISP) [CX0001] LM3S6110@TQFP100 [CX3021]  
LM3S6110@TQFP100(ISP) [CX0001] LM3S6112(new)@LQFP48 [CX3007]  
LM3S612(new)@LQFP48(ISP) [CX0001] LM3S612(old)@LQFP48 [CX3007]  
LM3S612(old)@LQFP48(ISP) [CX0001] LM3S613(new)@LQFP48 [CX3007]  
LM3S613(new)@LQFP48(ISP) [CX0001] LM3S613(old)@LQFP48 [CX3007]  
LM3S613(old)@LQFP48(ISP) [CX0001] LM3S615(new)@LQFP48 [CX3007]  
LM3S615(new)@LQFP48(ISP) [CX0001] LM3S615(old)@LQFP48 [CX3007]  
LM3S615(old)@LQFP48(ISP) [CX0001] LM3S617(new)@LQFP48 [CX3007]  
LM3S617(new)@LQFP48(ISP) [CX0001] LM3S617(old)@LQFP48 [CX3007]  
LM3S617(old)@LQFP48(ISP) [CX0001] LM3S618(new)@LQFP48 [CX3007]  
LM3S618(new)@LQFP48(ISP) [CX0001] LM3S618(old)@LQFP48 [CX3007]  
LM3S618(old)@LQFP48(ISP) [CX0001] LM3S628(new)@LQFP48 [CX3007]  
LM3S628(new)@LQFP48(ISP) [CX0001] LM3S628(old)@LQFP48 [CX3007]  
LM3S628(old)@LQFP48(ISP) [CX0001] LM3S6420@BGA108(ISP) [CX0001]  
LM3S6420@TQFP100(ISP) [CX0001] LM3S6420@TQFP100 [CX3021]  
LM3S6422@BGA108(ISP) [CX0001] LM3S6422@TQFP100(ISP) [CX0001]  
LM3S6432@BGA108(ISP) [CX0001] LM3S6432@TQFP100 [CX3021]  
LM3S6432@TQFP100(ISP) [CX0001] LM3S6537@BGA108(ISP) [CX0001]  
LM3S6537@TQFP100 [CX3021] LM3S6537@TQFP100(ISP) [CX0001]  
LM3S6610@BGA108(ISP) [CX0001] LM3S6610@TQFP100 [CX3021]  
LM3S6610@TQFP100(ISP) [CX0001] LM3S6611@BGA108(ISP) [CX0001]

LM3S6611@TQFP100 [CX3021]  
LM3S6618@BGA108(ISP) [CX0001]  
LM3S6618@TQFP100(ISP) [CX0001]  
LM3S6633@TQFP100 [CX3021]  
LM3S6637@BGA108(ISP) [CX0001]  
LM3S6637@TQFP100(ISP) [CX0001]  
LM3S6730@TQFP100 [CX3021]  
LM3S6753@BGA108(ISP) [CX0001]  
LM3S6753@TQFP100(ISP) [CX0001]  
LM3S6816@TQFP100 [CX3021]  
LM3S6911@BGA108(ISP) [CX0001]  
LM3S6911@TQFP100(ISP) [CX0001]  
LM3S6916@TQFP100 [CX3021]  
LM3S6918@BGA108(ISP) [CX0001]  
LM3S6918@TQFP100(ISP) [CX0001]  
LM3S6938@TQFP100 [CX3021]  
LM3S6950@BGA108(ISP) [CX0001]  
LM3S6950@TQFP100(ISP) [CX0001]  
LM3S6952@TQFP100 [CX3021]  
LM3S6965@BGA108(ISP) [CX0001]  
LM3S6965@TQFP100(ISP) [CX0001]  
LM3S800@LQFP48(ISP) [CX0001]  
LM3S801(new)@LQFP48(ISP) [CX0001]  
LM3S801(old)@LQFP48 [CX3007]  
LM3S801(old)@LQFP48(ISP) [CX0001]  
LM3S808@LQFP48 [CX3007]  
LM3S811(new)@LQFP48 [CX3007]  
LM3S811(new)@LQFP48(ISP) [CX0001]  
LM3S811(old)@LQFP48 [CX3007]  
LM3S811(old)@LQFP48(ISP) [CX0001]  
LM3S812(new)@LQFP48 [CX3007]  
LM3S812(new)@LQFP48(ISP) [CX0001]  
LM3S812(old)@LQFP48 [CX3007]  
LM3S812(old)@LQFP48(ISP) [CX0001]  
LM3S815(new)@LQFP48 [CX3007]  
LM3S815(new)@LQFP48(ISP) [CX0001]  
LM3S815(old)@LQFP48 [CX3007]  
LM3S815(old)@LQFP48(ISP) [CX0001]  
LM3S817(new)@LQFP48 [CX3007]  
LM3S817(new)@LQFP48(ISP) [CX0001]  
LM3S817(old)@LQFP48 [CX3007]  
LM3S817(old)@LQFP48(ISP) [CX0001]  
LM3S818(new)@LQFP48 [CX3007]  
LM3S818(new)@LQFP48(ISP) [CX0001]  
LM3S818(old)@LQFP48 [CX3007]  
LM3S818(old)@LQFP48(ISP) [CX0001]  
LM3S828(new)@LQFP48 [CX3007]  
LM3S828(new)@LQFP48(ISP) [CX0001]  
LM3S828(old)@LQFP48 [CX3007]  
LM3S828(old)@LQFP48(ISP) [CX0001]  
LM3S8530@BGA108(ISP) [CX0001]  
LM3S8530@TQFP100(ISP) [CX0001]  
LM3S8538@TQFP100 [CX3021]  
LM3S8630@BGA108(ISP) [CX0001]  
LM3S8630@TQFP100(ISP) [CX0001]  
LM3S8730@TQFP100 [CX3021]  
LM3S8733@BGA108(ISP) [CX0001]  
LM3S8733@TQFP100(ISP) [CX0001]  
LM3S8738@TQFP100 [CX3021]

LM3S6611@TQFP100(ISP) [CX0001]  
LM3S6618@TQFP100 [CX3021]  
LM3S6633@BGA108(ISP) [CX0001]  
LM3S6633@TQFP100(ISP) [CX0001]  
LM3S6637@TQFP100 [CX3021]  
LM3S6730@BGA108(ISP) [CX0001]  
LM3S6730@TQFP100(ISP) [CX0001]  
LM3S6753@TQFP100 [CX3021]  
LM3S6816@BGA108(ISP) [CX0001]  
LM3S6816@TQFP100(ISP) [CX0001]  
LM3S6911@TQFP100 [CX3021]  
LM3S6916@BGA108(ISP) [CX0001]  
LM3S6916@TQFP100(ISP) [CX0001]  
LM3S6918@TQFP100 [CX3021]  
LM3S6938@BGA108(ISP) [CX0001]  
LM3S6938@TQFP100(ISP) [CX0001]  
LM3S6950@TQFP100 [CX3021]  
LM3S6952@BGA108(ISP) [CX0001]  
LM3S6952@TQFP100(ISP) [CX0001]  
LM3S6965@TQFP100 [CX3021]  
LM3S800@LQFP48 [CX3007]  
LM3S801(new)@LQFP48 [CX3007]  
  
LM3S808@LQFP48(ISP) [CX0001]

LM3S8530@TQFP100 [CX3021]  
LM3S8538@BGA108(ISP) [CX0001]  
LM3S8538@TQFP100(ISP) [CX0001]  
LM3S8630@TQFP100 [CX3021]  
LM3S8730@BGA108(ISP) [CX0001]  
LM3S8730@TQFP100(ISP) [CX0001]  
LM3S8733@TQFP100 [CX3021]  
LM3S8738@BGA108(ISP) [CX0001]  
LM3S8738@TQFP100(ISP) [CX0001]

LM3S8930@BGA108(ISP) [CX0001]	LM3S8930@TQFP100 [CX3021]
LM3S8930@TQFP100(ISP) [CX0001]	LM3S8933@BGA108(ISP) [CX0001]
LM3S8933@TQFP100 [CX3021]	LM3S8933@TQFP100(ISP) [CX0001]
LM3S8938@BGA108(ISP) [CX0001]	LM3S8938@TQFP100 [CX3021]
LM3S8938@TQFP100(ISP) [CX0001]	LM3S8962@BGA108(ISP) [CX0001]
LM3S8962@TQFP100 [CX3021]	LM3S8962@TQFP100(ISP) [CX0001]
LM3S8970@BGA108(ISP) [CX0001]	LM3S8970@TQFP100 [CX3021]
LM3S8970@TQFP100(ISP) [CX0001]	LM3S8971@BGA108(ISP) [CX0001]
LM3S8971@TQFP100 [CX3021]	LM3S8971@TQFP100(ISP) [CX0001]

## LYONTEK

### E(E) PROM/FRAM/NVRAM

LY24C02 [CX0001]	LY24C02@SOIC8 [CX1045]
LY24C02@TSSOP8 [CX1059]	LY24C04 [CX0001]
LY24C04@SOIC8 [CX1045]	LY24C04@TSSOP8 [CX1059]
LY24C08 [CX0001]	LY24C08@SOIC8 [CX1045]
LY24C08@TSSOP8 [CX1059]	LY24C16 [CX0001]
LY24C16@SOIC8 [CX1045]	LY24C16@TSSOP8 [CX1059]

## MACRONIX

### E(E) PROM/FRAM/NVRAM

KH25L1005 [CX0001]	KH25L1005(ISP) [CX0001]
KH25L1005@SON8 [CX4005]	KH25L1005@SON8(ISP) [CX0001]
KH25L1005@SOP8 [CX1045]	KH25L1005@SOP8(ISP) [CX0001]
KH25L1005A [CX0001]	KH25L1005A@SON8 [CX4005#1]
KH25L1005A@SOP8 [CX1045#1]	KH25L12801F@SOP16 [CX1033#1]
KH25L12805D@SON8(Fast Mode) [CX4006#1]	
KH25L12805D@SOP16(Fast Mode) [CX1033#1]	
KH25L12805N@SOP16 [CX1033#1]	
KH25L12805N@SOP16(Fast Mode) [CX1033#1]	
KH25L12835F@SOP16 [CX1033#1]	KH25L12835F@SOP8 [CX1044#1]
KH25L12835F@WSON8(6*5mm) [CX4005#1]	
KH25L12835F@WSON8(8*6mm) [CX4006#1]	
KH25L12855F@TFBGA24(4*6) [CX5157]	
KH25L12855F@TFBGA24(5*5) [CX5146]	
KH25L1605@SON8 [CX4006#1]	
KH25L1605@SON8(Fast Mode) [CX4006#1]	
KH25L1605@SOP16 [CX1033#1]	
KH25L1605@SOP16(Fast Mode) [CX1033#1]	
KH25L1605A@SON8 [CX4006#1]	
KH25L1605A@SON8(Fast Mode) [CX4006#1]	
KH25L1605A@SOP16 [CX1033#1]	
KH25L1605A@SOP16(Fast Mode) [CX1033#1]	
KH25L1605A@SOP8 [CX1044#1]	
KH25L1605A@SOP8(Fast Mode) [CX1044#1]	
KH25L1605D@SON8 [CX4006#1]	
KH25L1605D@SON8(Fast Mode) [CX4006#1]	
KH25L1605D@SOP16 [CX1033#1]	
KH25L1605D@SOP16(Fast Mode) [CX1033#1]	
KH25L1605D@SOP8(150)(Fast Mode) [CX1045#1]	
KH25L1605D@SOP8(200)(Fast Mode) [CX1044#1]	
KH25L1606E [CX0001]	KH25L1606E(512bit) [CX0001]
KH25L1606E(512bit)@SOP16 [CX1033]	

KH25L1606E(512bit)@SOP8(150mil) [CX1045#1]  
KH25L1606E(512bit)@SOP8(200mil) [CX1044#1]  
KH25L1606E(512bit)@USON8 [CX4004#1]  
KH25L1606E(512bit)@WSON8 [CX4005#1]  
KH25L1606E@SOP16 [CX1033]  
KH25L1606E@SOP8(150 mil) [CX1045#1]  
KH25L1606E@SOP8(200 mil) [CX1044#1]  
KH25L1606E@USON8 [CX4004#1] KH25L1606E@WSON8 [CX4005#1]  
KH25L1636D@SOP16 [CX1033#1]  
KH25L1636D@SOP8(150mil) [CX1045#1]  
KH25L1636D@SOP8(200mil) [CX1044#1]  
KH25L1636D@WSON8 [CX4005#1] KH25L1673E@SOP8 [CX1044#1]  
KH25L2005 [CX0001] KH25L2005(ISP) [CX0001]  
KH25L2005@SON8 [CX4005] KH25L2005@SON8(ISP) [CX0001]  
KH25L2005@SOP8 [CX1045] KH25L2005@SOP8(ISP) [CX0001]  
KH25L2025 [CX0001] KH25L2025@SON8 [CX4005#1]  
KH25L2025@SOP8 [CX1045#1] KH25L3205@SOP16 [CX1033#1]  
KH25L3205@SOP16(Fast Mode) [CX1033#1]  
KH25L3205@SOP8 [CX1044#1]  
KH25L3205@SOP8(Fast Mode) [CX1044#1]  
KH25L3205A@SON8 [CX4006#1]  
KH25L3205A@SON8(Fast Mode) [CX4006#1]  
KH25L3205A@SOP16 [CX1033#1]  
KH25L3205A@SOP16(Fast Mode) [CX1033#1]  
KH25L3205A@SOP8 [CX1044#1]  
KH25L3205A@SOP8(Fast Mode) [CX1044#1]  
KH25L3205D@SON8(Fast Mode) [CX4006#1]  
KH25L3205D@SOP16 [CX1033#1]  
KH25L3205D@SOP16(Fast Mode) [CX1033#1]  
KH25L3205D@SOP8 [CX1044#1]  
KH25L3205D@SOP8(Fast Mode) [CX1044#1]  
KH25L3206E [CX1044#1] KH25L3206E(512bit) [CX0001]  
KH25L3206E(512bit)@SOP16 [CX1033#1]  
KH25L3206E(512bit)@SOP8 [CX1044#1]  
KH25L3206E(512bit)@USON8 [CX4004#1]  
KH25L3206E(512bit)@WSON8 [CX4005#1]  
KH25L3206E@SOP16 [CX1033#1] KH25L3206E@SOP8 [CX1044#1]  
KH25L3206E@USON8 [CX4004#1] KH25L3206E@WSON8 [CX4005#1]  
KH25L3236D@SOP16 [CX1033#1]  
KH25L3236D@SOP8(150mil) [CX1045#1]  
KH25L3236D@SOP8(200mil) [CX1044#1]  
KH25L3236D@WSON8 [CX4005#1] KH25L3239E@SOP8 [CX1044#1]  
KH25L3239E@VSOP8 [CX1044#1] KH25L3239E@WSON8 [CX4005#1]  
KH25L3273E@SOP16 [CX1033#1] KH25L3273E@SOP8 [CX1044#1]  
KH25L3273E@VSOP8 [CX1044#1] KH25L3273E@WSON8 [CX4005#1]  
KH25L4005 [CX0001] KH25L4005(150mil)@SOP8 [CX1045]  
KH25L4005(150mil)@SOP8(ISP) [CX0001]  
KH25L4005(209mil)@SOP8 [CX1044]  
KH25L4005(209mil)@SOP8(ISP) [CX0001]  
KH25L4005(ISP) [CX0001] KH25L4005@SON8 [CX4005]  
KH25L4005@SON8(ISP) [CX0001] KH25L4005A [CX0001]  
KH25L4005A(150mil)@SOP8 [CX1045]  
KH25L4005A(150mil)@SOP8(ISP) [CX0001]  
KH25L4005A(209mil)@SOP8 [CX1044]  
KH25L4005A(209mil)@SOP8(ISP) [CX0001]  
KH25L4005A(ISP) [CX0001] KH25L4005A@SON8 [CX4005]  
KH25L4005A@SON8(ISP) [CX0001] KH25L4006E [CX0001]  
KH25L4006E@SOP8(150mil) [CX1045#1]  
KH25L4006E@SOP8(200mil) [CX1044#1]

KH25L4006E@WSON8 [CX4005#1] KH25L4025A [CX0001]  
KH25L4025A(150mil)@SOP8 [CX1045#1]  
KH25L4025A(209mil)@SOP8 [CX1044#1]  
KH25L4025A@SON8 [CX4005#1] KH25L512@SON8 [CX4005#1]  
KH25L512@SOP8 [CX1045#1] KH25L512A [CX0001]  
KH25L512A@SON8 [CX4005#1] KH25L512A@SOP8 [CX1045#1]  
KH25L6405@SOP16 [CX1033#1]  
KH25L6405@SOP16(Fast Mode) [CX1033#1]  
KH25L6405@SOP8 [CX1044#1]  
KH25L6405@SOP8(Fast Mode) [CX1044#1]  
KH25L6405D@SON8(Fast Mode) [CX4006#1]  
KH25L6405D@SOP16 [CX1033#1]  
KH25L6405D@SOP16(Fast Mode) [CX1033#1]  
KH25L6405D@SOP8 [CX1044#1] KH25L6405MC@SOP16 [CX1033#1]  
KH25L6405MC@SOP8 [CX1044#1] KH25L6406E@SOP16 [CX1033#1]  
KH25L6406E@SOP8 [CX1044#1] KH25L6406E@WSON8 [CX4006#1]  
KH25L6455E@SOP16 [CX1033#1] KH25L6455E@SOP8 [CX1044#1]  
KH25L6455E@TFBGA24 [CX5146] KH25L6473E@SOP16 [CX1033#1]  
KH25L6473E@SOP8 [CX1044#1] KH25L6473E@VSOP8 [CX1044#1]  
KH25L6473E@WSON8 [CX4005#1] KH25L8005 [CX0001]  
KH25L8005(150mil)@SOP8 [CX1045#1]  
KH25L8005(150mil)@SOP8(ISP) [CX0001]  
KH25L8005(209mil)@SOP8 [CX1044#1]  
KH25L8005(209mil)@SOP8(ISP) [CX0001]  
KH25L8005(ISP) [CX0001] KH25L8005@SON8 [CX4005#1]  
KH25L8005@SON8(ISP) [CX0001] KH25L8006E [CX0001]  
KH25L8006E(512bit) [CX0001]  
KH25L8006E(512bit)@SOP8(150mil) [CX1045#1]  
KH25L8006E(512bit)@SOP8(200mil) [CX1044#1]  
KH25L8006E(512bit)@USON8 [CX4004#1]  
KH25L8006E(512bit)@WSON8 [CX4005#1]  
KH25L8006E@SOP8(150 mil) [CX1045#1]  
KH25L8006E@SOP8(200 mil) [CX1044#1]  
KH25L8006E@USON8 [CX4004#1] KH25L8006E@WSON8 [CX4005#1]  
KH25L8025 [CX0001]  
KH25L8025(150mil)@SOP8 [CX1045#1]  
KH25L8025(209mil)@SOP8 [CX1044#1]  
KH25L8025@SON8 [CX4005#1] KH25L8036D [CX0001]  
KH25L8036D@SOP16 [CX1033] KH25L8036D@SOP8(150mil) [CX1045]  
KH25L8036D@SOP8(200mil) [CX1044] KH25L8036D@WSON8 [CX4005]  
KH25L8073E@SOP8 [CX1044#1] KH25U6439F@SOP8 [CX1044#1]  
KH25U6439F@VSOP8 [CX1044#1] KH25U6439F@WSON8 [CX4005#1]  
KH29GL128FHT2@TSOP56 [CX1011] KH29GL128FHXF@FBGA64 [CX5074]  
KH29GL128FLT2@TSOP56 [CX1011] KH29GL128FLXF@FBGA64 [CX5074]  
KH29GL256FHT2@TSOP56 [CX1011] KH29GL256FHXF@FBGA64 [CX5074]  
KH29GL256FLT2@TSOP56 [CX1011] KH29GL256FLXF@FBGA64 [CX5074]  
KH29GL512FHT2@TSOP56 [CX1011] KH29GL512FHXF@FBGA64 [CX5074]  
KH29GL512FLT2@TSOP56 [CX1011] KH29GL512FLXF@FBGA64 [CX5074]  
KH29GL640EB@TSOP48 [CX1004] KH29GL640ET@TSOP48 [CX1004]  
KH29LV004CB@PLCC32 [CX2032] KH29LV004CB@TSOP40 [CX1006]  
KH29LV004CT@PLCC32 [CX2032] KH29LV004CT@TSOP40 [CX1006]  
KH29LV008CB@TSOP40 [CX1006] KH29LV008CT@TSOP40 [CX1006]  
KH29LV040C [CX0001] KH29LV040C@PLCC32 [CX2032]  
KH29LV160CBT@TSOP48 [CX1004] KH29LV160CTT@TSOP48 [CX1004]  
KH29LV160DBT@TSOP48 [CX1004] KH29LV160DTT@TSOP48 [CX1004]  
KH29LV320CBT@TSOP48 [CX1004] KH29LV320CTT@TSOP48 [CX1004]  
KH29LV320DBT@TSOP48 [CX1004] KH29LV320DTT@TSOP48 [CX1004]  
KH29LV320EBT@TSOP48 [CX1004] KH29LV320ETT@TSOP48 [CX1004]  
KH29LV400CBT@TSOP48 [CX1004] KH29LV400CTT@TSOP48 [CX1004]

KH29LV640DBT@TSOP48 [CX1004]                    KH29LV640DTT@TSOP48 [CX1004]  
KH29LV800CBT@TSOP48 [CX1004]                    KH29LV800CTT@TSOP48 [CX1004]  
KH29SV400CBT@TSOP48 [CX1004]                    KH29SV400CTT@TSOP48 [CX1004]  
KH68GL1G0FHT2@TSOP56 [CX1011]                   KH68GL1G0FHXF@FBGA64 [CX5074]  
KH68GL1G0FLT2@TSOP56 [CX1011]                   KH68GL1G0FLXF@FBGA64 [CX5074]  
MX25L1005 [CX0001]                                MX25L1005(ISP) [CX0001]  
MX25L1005@SON8 [CX4005]                         MX25L1005@SON8(ISP) [CX0001]  
MX25L1005@SOP8 [CX1045]                         MX25L1005@SOP8(ISP) [CX0001]  
MX25L1005@USON8 [CX4002]                        MX25L1005A [CX0001]  
MX25L1005A@SON8 [CX4005#1]                     MX25L1005A@SOP8 [CX1045#1]  
MX25L1005C@SOP8 [CX1045]                        MX25L1005C@USON8 [CX4002]  
MX25L1006E@SOP8 [CX1045#1]                     MX25L1006E@USON8 [CX4002#1]  
MX25L1006E@WLCSP8 [CX5227#1]                   MX25L1021E@SOP8 [CX1045#1]  
MX25L1025C@SOP8 [CX1045#1]                     MX25L1026E@SOP8 [CX1045#1]  
MX25L12801F@SOP16 [CX1033#1]  
MX25L12801F@SOP16(Fast Mode) [CX1033#1]  
MX25L12805D@SON8(Fast Mode) [CX4006#1]  
MX25L12805D@SOP16(512bit OTP) [CX1033#1]  
MX25L12805D@SOP16(Fast Mode) [CX1033#1]  
MX25L12805D@WSON8(512bit OTP) [CX4006#1]  
MX25L12805N@SOP16 [CX1033#1]  
MX25L12805N@SOP16(Fast Mode) [CX1033#1]  
MX25L12835E@SOP16 [CX1033#1]                    MX25L12835E@WSON8 [CX4006#1]  
MX25L12835F@SOP16 [CX1033#1]                    MX25L12835F@SOP8 [CX1044#1]  
MX25L12835F@WSON8(6\*5mm) [CX4005#1]  
MX25L12835F@WSON8(8\*6mm) [CX4006#1]  
MX25L12836E@SOP16 [CX1033#1]                    MX25L12836E@SOP8 [CX1044#1]  
MX25L12836E@WSON8 [CX4006#1]                    MX25L12845E@SOP16 [CX1033#1]  
MX25L12845E@WSON8 [CX4006#1]                    MX25L12845E@WSON8(\*) [CX4006#1]  
MX25L12855E@SOP16 [CX1033#1]                    MX25L12855E@TFBGA24 [CX5146]  
MX25L12855E@TFBGA24(SINAEN) [CX5146]  
MX25L12855F@TFBGA24(4\*6) [CX5157]  
MX25L12855F@TFBGA24(5\*5) [CX5146]  
MX25L12865E@SOP16 [CX1033#1]                    MX25L12865E@SOP8 [CX1044#1]  
MX25L12865E@WSON8 [CX4006#1]                    MX25L12873F@SOP16 [CX1033#1]  
MX25L12873F@SOP8 [CX1044#1]                    MX25L12873F@WSON8 [CX4005#1]  
MX25L12875E@SOP16 [CX1033#1]                    MX25L12875E@SOP8 [CX1044#1]  
MX25L12875E@WSON8 [CX4006#1]                    MX25L1605@SON8 [CX4006#1]  
MX25L1605@SON8(Fast Mode) [CX4006#1]  
MX25L1605@SOP16 [CX1033#1]  
MX25L1605@SOP16(Fast Mode) [CX1033#1]  
MX25L1605A@SON8 [CX4006#1]  
MX25L1605A@SON8(Fast Mode) [CX4006#1]  
MX25L1605A@SOP16 [CX1033#1]  
MX25L1605A@SOP16(Fast Mode) [CX1033#1]  
MX25L1605A@SOP8 [CX1044#1]  
MX25L1605A@SOP8(Fast Mode) [CX1044#1]  
MX25L1605D(512bit OTP) [CX0001]                 MX25L1605D@SON8 [CX4006#1]  
MX25L1605D@SON8(Fast Mode) [CX4006#1]  
MX25L1605D@SOP16 [CX1033#1]  
MX25L1605D@SOP16(512bit OTP) [CX1033#1]  
MX25L1605D@SOP16(Fast Mode) [CX1033#1]  
MX25L1605D@SOP8(150)(Fast Mode) [CX1045#1]  
MX25L1605D@SOP8(200)(Fast Mode) [CX1044#1]  
MX25L1605D@SOP8(512bit OTP)(150) [CX1045#1]  
MX25L1605D@SOP8(512bit OTP)(200) [CX1044#1]  
MX25L1605D@USON8 [CX4004#1]  
MX25L1605D@USON8(512bit OTP) [CX4004#1]  
MX25L1605D@USON8(Fast Mode) [CX4004#1]

MX25L1605D@WSON8(512bit OTP) [CX4005#1]  
MX25L1606E [CX0001] MX25L1606E(512bit) [CX0001]  
MX25L1606E(512bit)@SOP16 [CX1033]  
MX25L1606E(512bit)@SOP8(150mil) [CX1045#1]  
MX25L1606E(512bit)@SOP8(200mil) [CX1044#1]  
MX25L1606E(512bit)@USON8 [CX4004#1]  
MX25L1606E(512bit)@WSON8 [CX4005#1]  
MX25L1606E@SOP16 [CX1033]  
MX25L1606E@SOP8(150 mil) [CX1045#1]  
MX25L1606E@SOP8(200 mil) [CX1044#1]  
MX25L1606E@USON8 [CX4004#1] MX25L1606E@WSON8 [CX4005#1]  
MX25L1608D [CX0001] MX25L1608D@SOP16 [CX1033#1]  
MX25L1608D@SOP8(150mil) [CX1045#1]  
MX25L1608D@SOP8(200mil) [CX1044#1]  
MX25L1608D@USON8 [CX4004#1] MX25L1608D@WSON8 [CX4005#1]  
MX25L1608E@SOP8(150mil) [CX1045#1]  
MX25L1608E@SOP8(200mil) [CX1044#1]  
MX25L1615D@SOP16 [CX1033#1] MX25L1615D@SOP8 [CX1044#1]  
MX25L1633E@SOP16 [CX1033#1] MX25L1633E@SOP8 [CX1044#1]  
MX25L1633E@WSON8 [CX4005#1] MX25L1635D@SOP16 [CX1033#1]  
MX25L1635D@SOP8(150mil) [CX1045#1]  
MX25L1635D@SOP8(200mil) [CX1044#1]  
MX25L1635D@WSON8 [CX4005#1] MX25L1635E@SOP8 [CX1044#1]  
MX25L1636D@SOP16 [CX1033#1]  
MX25L1636D@SOP8(150mil) [CX1045#1]  
MX25L1636D@SOP8(200mil) [CX1044#1]  
MX25L1636D@WSON8 [CX4005#1] MX25L1636E@SOP8 [CX1044#1]  
MX25L1655D@SOP8 [CX1044#1]  
MX25L1655D@SOP8[512 bit] [CX1044#1]  
MX25L1655D@TBGA24 [CX5146]  
MX25L1655D@TBGA24[512 bit] [CX5146]  
MX25L1673E@SOP8 [CX1044#1] MX25L1675E@SOP8 [CX1044#1]  
MX25L1675E@WSON8 [CX4005#1] MX25L2005 [CX0001]  
MX25L2005(ISP) [CX0001] MX25L2005@SON8 [CX4005]  
MX25L2005@SON8(ISP) [CX0001] MX25L2005@SOP8 [CX1045]  
MX25L2005@SOP8(ISP) [CX0001] MX25L2005C@SOP8 [CX1045]  
MX25L2005C@USON8 [CX4005] MX25L2006E@SOP8 [CX1045#1]  
MX25L2006E@WSON8 [CX4005#1] MX25L2025 [CX0001]  
MX25L2025@SON8 [CX4005#1] MX25L2025@SOP8 [CX1045#1]  
MX25L2026C@SOP8 [CX1045#1] MX25L2026E@SOP8 [CX1045#1]  
MX25L2026E@WSON8 [CX4005#1] MX25L25635E@SOP16 [CX1033#1]  
MX25L25635E@WSON8 [CX4006#1] MX25L25635F@SOP16 [CX1033#1]  
MX25L25635F@WSON8 [CX4006#1] MX25L25636E@SOP16 [CX1033#1]  
MX25L25639F@WSON8 [CX4006#1] MX25L25655E@SOP16 [CX1033#1]  
MX25L25655E@TFBGA24 [CX5146] MX25L25655F@SOP16 [CX1033#1]  
MX25L25655F@TFBGA24[4\*6] [CX5146]  
MX25L25655F@TFBGA24[5\*5] [CX5157]  
MX25L25735E@SOP16 [CX1033#1] MX25L25735E@WSON8 [CX4006#1]  
MX25L25735F@SOP16 [CX1033#1] MX25L25735F@WSON8 [CX4006#1]  
MX25L25835E@SOP16 [CX1033#1] MX25L3205@SOP16 [CX1033#1]  
MX25L3205@SOP16(Fast Mode) [CX1033#1]  
MX25L3205@SOP8 [CX1044#1]  
MX25L3205@SOP8(Fast Mode) [CX1044#1]  
MX25L3205A@SON8 [CX4006#1]  
MX25L3205A@SON8(Fast Mode) [CX4006#1]  
MX25L3205A@SOP16 [CX1033#1]  
MX25L3205A@SOP16(Fast Mode) [CX1033#1]  
MX25L3205A@SOP8 [CX1044#1]  
MX25L3205A@SOP8(Fast Mode) [CX1044#1]



MX25L3205D(512bit OTP) [CX0001]  
MX25L3205D@SON8(Fast Mode) [CX4006#1]  
MX25L3205D@SOP16 [CX1033#1]  
MX25L3205D@SOP16(512bit OTP) [CX1033#1]  
MX25L3205D@SOP16(Fast Mode) [CX1033#1]  
MX25L3205D@SOP8 [CX1044#1]  
MX25L3205D@SOP8(512bit OTP) [CX1044#1]  
MX25L3205D@SOP8(Fast Mode) [CX1044#1]  
MX25L3205D@USON8 [CX4004#1]  
MX25L3205D@USON8(512bit OTP) [CX4004#1]  
MX25L3205D@USON8(Fast Mode) [CX4004#1]  
MX25L3205D@WSON8(512bit OTP) [CX4005#1]  
MX25L3206E [CX1044#1] MX25L3206E(512bit) [CX0001]  
MX25L3206E(512bit)@SOP16 [CX1033#1]  
MX25L3206E(512bit)@SOP8 [CX1044#1]  
MX25L3206E(512bit)@USON8 [CX4004#1]  
MX25L3206E(512bit)@WSON8 [CX4005#1]  
MX25L3206E@SOP16 [CX1033#1] MX25L3206E@SOP8 [CX1044#1]  
MX25L3206E@USON8 [CX4004#1] MX25L3206E@WSON8 [CX4005#1]  
MX25L3208D [CX0001] MX25L3208D@SOP16 [CX1033#1]  
MX25L3208D@SOP8 [CX1044#1] MX25L3208D@USON8 [CX4004#1]  
MX25L3208D@WSON8 [CX4005#1] MX25L3208E@SOP8 [CX1044#1]  
MX25L3215D@SOP16 [CX1033#1] MX25L3215D@SOP8 [CX1044#1]  
MX25L3225D@SOP8 [CX1044#1] MX25L3235D@SOP16 [CX1033#1]  
MX25L3235D@SOP8 [CX1044#1] MX25L3235D@WSON8 [CX4005#1]  
MX25L3235E@SOP8 [CX1044#1] MX25L3235E@WSON8 [CX4005#1]  
MX25L3236D@SOP16 [CX1033#1]  
MX25L3236D@SOP8(150mil) [CX1045#1]  
MX25L3236D@SOP8(200mil) [CX1044#1]  
MX25L3236D@WSON8 [CX4005#1] MX25L3237D@SOP16 [CX1033#1]  
MX25L3237D@WSON8 [CX4005#1] MX25L3239E@SOP8 [CX1044#1]  
MX25L3239E@VSOP8 [CX1044#1] MX25L3239E@WSON8 [CX4005#1]  
MX25L3254E@SOP8[4K bit] [CX1044#1]  
MX25L3254E@TFBGA24[5\*5] [CX5157] MX25L3254E@TFBGA24[6\*4] [CX5146]  
MX25L3255D@SOP8 [CX1044#1]  
MX25L3255D@SOP8[4K bit] [CX1044#1]  
MX25L3255D@TBGA24 [CX5146]  
MX25L3255D@TBGA24[4K bit] [CX5146]  
MX25L3255E@SOP8 [CX1044#1]  
MX25L3255E@SOP8[4K bit] [CX1044#1]  
MX25L3255E@TBGA24 [CX5146] MX25L3255E@TFBGA24[5\*5] [CX5157]  
MX25L3255E@TFBGA24[6\*4] [CX5146] MX25L3273E@SOP16 [CX1033#1]  
MX25L3273E@SOP8 [CX1044#1] MX25L3273E@VSOP8 [CX1044#1]  
MX25L3273E@WSON8 [CX4005#1] MX25L3275E@SOP16 [CX1033#1]  
MX25L3275E@SOP8 [CX1044#1] MX25L3275E@WSON8 [CX4005#1]  
MX25L4005 [CX0001] MX25L4005(150mil)@SOP8 [CX1045]  
MX25L4005(150mil)@SOP8(ISP) [CX0001]  
MX25L4005(209mil)@SOP8 [CX1044]  
MX25L4005(209mil)@SOP8(ISP) [CX0001]  
MX25L4005(ISP) [CX0001] MX25L4005@SON8 [CX4005]  
MX25L4005@SON8(ISP) [CX0001] MX25L4005A [CX0001]  
MX25L4005A(150mil)@SOP8 [CX1045]  
MX25L4005A(150mil)@SOP8(ISP) [CX0001]  
MX25L4005A(209mil)@SOP8 [CX1044]  
MX25L4005A(209mil)@SOP8(ISP) [CX0001]  
MX25L4005A(ISP) [CX0001] MX25L4005A@SON8 [CX4005]  
MX25L4005A@SON8(ISP) [CX0001] MX25L4005A@USON8 [CX4004]  
MX25L4005C [CX0001] MX25L4005C@SOP8 [CX1045]  
MX25L4005C@TSSOP8 [CX1044] MX25L4005C@USON8 [CX4005]

MX25L4006E [CX0001]  
MX25L4006E@SOP8(150mil) [CX1045#1]  
MX25L4006E@SOP8(200mil) [CX1044#1]  
MX25L4006E@WSON8 [CX4005#1]                   MX25L4025@SOP8 [CX1045]  
MX25L4025A [CX0001]  
MX25L4025A(150mil)@SOP8 [CX1045#1]  
MX25L4025A(209mil)@SOP8 [CX1044#1]  
MX25L4025A@SON8 [CX4005#1]                   MX25L4026D@SOP8 [CX1045#1]  
MX25L4026E@SOP8 [CX1045#1]                   MX25L512@SON8 [CX4005#1]  
MX25L512@SOP8 [CX1045#1]                   MX25L512@USON8 [CX4002#1]  
MX25L5121E@SOP8 [CX1045#1]                   MX25L5121E@TSSOP8 [CX1059#1]  
MX25L512A [CX0001]                   MX25L512A@SON8 [CX4005#1]  
MX25L512A@SOP8 [CX1045#1]                   MX25L512C [CX0001]  
MX25L512C@TSSOP8 [CX1059#3]                   MX25L512C@USON8 [CX4002#1]  
MX25L512E@SOP8 [CX1045#1]                   MX25L512E@TSSOP8 [CX1059#1]  
MX25L512E@USON8 [CX4002#1]                   MX25L6405@SOP16 [CX1033#1]  
MX25L6405@SOP16(Fast Mode) [CX1033#1]  
MX25L6405@SOP8 [CX1044#1]  
MX25L6405@SOP8(Fast Mode) [CX1044#1]  
MX25L6405D@SON8(Fast Mode) [CX4006#1]  
MX25L6405D@SOP16 [CX1033#1]  
MX25L6405D@SOP16(512bit OTP) [CX1033#1]  
MX25L6405D@SOP16(Fast Mode) [CX1033#1]  
MX25L6405D@SOP8 [CX1044#1]  
MX25L6405D@WSON8(512bit OTP) [CX4006#1]  
MX25L6405MC@SOP16 [CX1033#1]                   MX25L6405MC@SOP8 [CX1044#1]  
MX25L6406E@SOP16 [CX1033#1]                   MX25L6406E@SOP8 [CX1044#1]  
MX25L6406E@WSON8 [CX4006#1]                   MX25L6408D@SOP16 [CX1033#1]  
MX25L6408D@WSON8 [CX4006#1]                   MX25L6408E@SOP16 [CX1033#1]  
MX25L6408E@SOP8 [CX1044#1]                   MX25L6415D@SOP16 [CX1033#1]  
MX25L6415D@SOP8 [CX1044#1]                   MX25L6435E@SOP8 [CX1044#1]  
MX25L6435E@WSON8 [CX4006#1]                   MX25L6436E@SOP16 [CX1033#1]  
MX25L6436E@SOP8 [CX1044#1]                   MX25L6436E@WSON8 [CX4006#1]  
MX25L6439F@SOP8 [CX1044#1]                   MX25L6439F@VSOP8 [CX1044#1]  
MX25L6445E@SOP16 [CX1033#1]  
MX25L6445E@SOP16(4K bit OTP) [CX1033#1]  
MX25L6445E@SOP8 [CX1044#1]  
MX25L6445E@SOP8(4K bit OTP) [CX1044#1]  
MX25L6445E@WSON8 [CX4006#1]  
MX25L6445E@WSON8(4K bit OTP) [CX4006#1]  
MX25L6446E@SOP16 [CX1033#1]                   MX25L6446E@SOP8 [CX1044#1]  
MX25L6446E@WSON8 [CX4006#1]                   MX25L6455E@SOP16 [CX1033#1]  
MX25L6455E@SOP8 [CX1044#1]                   MX25L6455E@TFBGA24 [CX5146]  
MX25L6456E@SOP8 [CX1044#1]                   MX25L6456E@TFBGA24(4\*6) [CX5146]  
MX25L6456E@TFBGA24(5\*5) [CX5157]                   MX25L6465E@SOP16 [CX1033#1]  
MX25L6465E@SOP8 [CX1044#1]                   MX25L6465E@WSON8 [CX4006#1]  
MX25L6473E@SOP16 [CX1033#1]                   MX25L6473E@SOP8 [CX1044#1]  
MX25L6473E@VSOP8 [CX1044#1]                   MX25L6473E@WSON8 [CX4005#1]  
MX25L6475E@SOP16 [CX1033#1]                   MX25L6475E@SOP8 [CX1044#1]  
MX25L6475E@WSON8 [CX4005#1]                   MX25L8005 [CX0001]  
MX25L8005(150mil)@SOP8 [CX1045]  
MX25L8005(150mil)@SOP8(ISP) [CX0001]  
MX25L8005(209mil)@SOP8 [CX1044]  
MX25L8005(209mil)@SOP8(ISP) [CX0001]  
MX25L8005(ISP) [CX0001]                   MX25L8005@SON8 [CX4005]  
MX25L8005@SON8(ISP) [CX0001]                   MX25L8005@USON8 [CX4004]  
MX25L8006E [CX0001]                   MX25L8006E(512bit) [CX0001]  
MX25L8006E(512bit)@SOP8(150mil) [CX1045#1]  
MX25L8006E(512bit)@SOP8(200mil) [CX1044#1]

MX25L8006E(512bit)@USON8 [CX4004#1]  
MX25L8006E(512bit)@WSON8 [CX4005#1]  
MX25L8006E@SOP8(150 mil) [CX1045#1]  
MX25L8006E@SOP8(200 mil) [CX1044#1]  
MX25L8006E@SOP8(DELTA) [CX1045#1]  
MX25L8006E@USON8 [CX4004#1]                   MX25L8006E@WSON8 [CX4005#1]  
MX25L8025 [CX0001]  
MX25L8025(150mil)@SOP8 [CX1045#1]  
MX25L8025(209mil)@SOP8 [CX1044#1]  
MX25L8025@SON8 [CX4005#1]                   MX25L8035E@SOP8 [CX1044#1]  
MX25L8036D [CX0001]                   MX25L8036D@SOP16 [CX1033]  
MX25L8036D@SOP8(150mil) [CX1045]                   MX25L8036D@SOP8(200mil) [CX1044]  
MX25L8036D@WSON8 [CX4005]                   MX25L8036E@SOP8 [CX1044#1]  
MX25L8073E@SOP8 [CX1044#1]                   MX25L8075E@SOP8 [CX1044#1]  
MX25U12835F@SOP16 [CX1033#1]                   MX25U12835F@USON8 [CX4005#1]  
MX25U12835F@WSON8 [CX4006#1]                   MX25U1635@SOIC8 [CX1045#1]  
MX25U1635@USON8(4\*4mm) [CX4004#1]  
MX25U1635@USON8(6\*5mm) [CX4005#1]  
MX25U1635E@SOP8(150mil) [CX1045#1]  
MX25U1635E@SOP8(200mil) [CX1044#1]  
MX25U1635E@USON8 [CX4004#1]                   MX25U1635E@WSON8 [CX4005#1]  
MX25U2032E@SOP8 [CX1045#1]                   MX25U2032E@USON8 [CX4004#1]  
MX25U2032E@WSON8 [CX4005#1]                   MX25U2033E@SOP8 [CX1045#1]  
MX25U2033E@USON8 [CX4004#1]                   MX25U2033E@WSON8 [CX4005#1]  
MX25U25635E@SOP16 [CX1033#1]                   MX25U25635E@WSON8 [CX4006#1]  
MX25U3235E@SOP8(150mil) [CX1045#1]  
MX25U3235E@SOP8(200mil) [CX1044#1]  
MX25U3235E@USON8 [CX4004#1]                   MX25U3235E@WSON8 [CX4005#1]  
MX25U3235F@SOP8 [CX1044#1]                   MX25U3235F@WSON8 [CX4005#1]  
MX25U4032E@SOP8 [CX1045#1]                   MX25U4032E@USON8 [CX4004#1]  
MX25U4032E@WSON8 [CX4005#1]                   MX25U4033E@SOP8 [CX1045#1]  
MX25U4033E@USON8 [CX4004#1]                   MX25U4033E@WSON8 [CX4005#1]  
MX25U4035@SOIC8 [CX1045#1]  
MX25U4035@USON8(4\*4mm) [CX4004#1]  
MX25U4035@USON8(6\*5mm) [CX4005#1]  
MX25U6435E@WSON8 [CX4005#1]                   MX25U6435F@SOP8 [CX1044#1]  
MX25U6435F@WSON8 [CX4005#1]                   MX25U6439F@SOP8 [CX1044#1]  
MX25U6439F@VSOP8 [CX1044#1]                   MX25U6439F@WSON8 [CX4005#1]  
MX25U8033E@SOP8(150mil) [CX1045#1]  
MX25U8033E@SOP8(200mil) [CX1044#1]  
MX25U8033E@USON8 [CX4004#1]                   MX25U8033E@WSON8 [CX4005#1]  
MX25U8035@SOIC8 [CX1045#1]  
MX25U8035@USON8(4\*4mm) [CX4004#1]  
MX25U8035@USON8(6\*5mm) [CX4005#1]  
MX25U8035E@SOP8(150mil) [CX1045#1]  
MX25U8035E@SOP8(200mil) [CX1044#1]  
MX25U8035E@USON8 [CX4004#1]                   MX25U8035E@WSON8 [CX4005#1]  
MX25V1006E@TSSOP8 [CX1059#1]                   MX25V1006E@USON8 [CX4002#1]  
MX25V2006E@SOP8 [CX1045#1]                   MX25V2006E@WSON8 [CX4005#1]  
MX25V4005 [CX0001]                   MX25V4005@USON8 [CX4005]  
MX25V4005C@SOP8 [CX0001]                   MX25V4005C@WSON8 [CX4005]  
MX25V4006E@SOP8 [CX1045#1]                   MX25V4006E@WSON8 [CX4005#1]  
MX25V4035@SOP8 [CX1045#1]                   MX25V4035@WSON8 [CX4005#1]  
MX25V512@USON8 [CX4002#1]                   MX25V512C@TSSOP8 [CX1059#3]  
MX25V512C@USON8 [CX4002#1]                   MX25V512E@SOP8 [CX1045#1]  
MX25V512E@USON8 [CX4002#1]                   MX25V8005@SOP8 [CX1045]  
MX25V8005@WSON8 [CX4005]  
MX25V8006E(512bit)@SOP8 [CX1045#1]  
MX25V8006E(512bit)@WSON8 [CX4005#1]

MX25V8006E@SOP8 [CX1045#1]  
MX25V8035@SOP8 [CX1045#1]  
MX26C1000 [CX0001]  
MX26C1000@SOIC32 [CX1034]  
MX26C1000B [CX0001]  
MX26C1000B@SOIC32 [CX1019]  
MX26C2000B [CX0001]  
MX26C2000B@SOIC32 [CX1019]  
MX26C512A [CX0001]  
MX26C512A@SOIC28 [CX1035]  
MX26F128J3TC@TSOP56 [CX1011]  
MX26F640J3TC@TSOP56 [CX1055]  
MX26L12711MC@PSOP44 [CX1014]  
MX26L6419T@TSOP48 [CX1004]  
MX26L6420@TSOP48 [CX1001]  
MX26LV004B@TSOP40 [CX1006]  
MX26LV004T@TSOP40 [CX1006]  
MX26LV008T@TSOP40 [CX1006]  
MX26LV040@PLCC32 [CX2032]  
MX26LV160BT@TSOP48 [CX1043]  
MX26LV160BX(0.4)@CSP48 [CX5002]  
MX26LV160TX(0.3)@CSP48 [CX5002]  
MX26LV400BT@TSOP48 [CX1043]  
MX26LV400BX(0.4)@CSP48 [CX5002]  
MX26LV400TX(0.3)@CSP48 [CX5002]  
MX26LV800BM@PSOP44 [CX1014]  
MX26LV800BX(0.3)@CSP48 [CX5002]  
MX26LV800TM@PSOP44 [CX1014]  
MX26LV800TX(0.3)@CSP48 [CX5002]  
MX27C1000 [CX0001]  
MX27C1000@SOIC32 [CX1034]  
MX27C1000A [CX0001]  
MX27C1000A@SOIC32 [CX1034]  
MX27C1001 [CX0001]  
MX27C1001@SOIC32 [CX1034]  
MX27C1024 [CX0001]  
MX27C1024@SOP40 [CX1022]  
MX27C1024A [CX0001]  
MX27C1024A@SOP40 [CX1022]  
MX27C1024B [CX0001]  
MX27C1024B@SOP40 [CX1022]  
MX27C1100 [CX0001]  
MX27C2000 [CX0001]  
MX27C2000@SOIC32 [CX1034]  
MX27C2000A [CX0001]  
MX27C2000A@SOIC32 [CX1034]  
MX27C2048 [CX0001]  
MX27C2048@VSOP40 [CX1005]  
MX27C256 [CX0001]  
MX27C4000 [CX0001]  
MX27C4000@SOIC32 [CX1034]  
MX27C4000A [CX0001]  
MX27C4000A@SOIC32 [CX1034]  
MX27C4096 [CX0001]  
MX27C4100 [CX0001]  
MX27C512 [CX0001]  
MX27C516 [CX0001]  
MX27C516@VSOP40 [CX1005]  
MX27C8000@PLCC32 [CX2032]

MX25V8006E@WSON8 [CX4005#1]  
MX25V8035@WSON8 [CX4005#1]  
MX26C1000@PLCC32 [CX2032]  
MX26C1000@TSOP32 [CX1002]  
MX26C1000B@PLCC32 [CX2032]  
MX26C1000B@TSOP32 [CX1002]  
MX26C2000B@PLCC32 [CX2032]  
MX26C2000B@TSOP32 [CX1002]  
MX26C512A@PLCC32 [CX2032]  
MX26C512A@TSOP28 [CX1024]  
MX26F128J3XC@CSP64 [CX5004]  
MX26F640J3XC@CSP64 [CX5004]  
MX26L12811MC@PSOP44 [CX1014]  
MX26L6420@PSOP44 [CX1014]  
MX26LV004B@PLCC32 [CX2032]  
MX26LV004T@PLCC32 [CX2032]  
MX26LV008B@TSOP40 [CX1006]  
MX26LV040 [CX0001]  
MX26LV040@TSOP32 [CX1002]  
MX26LV160BX(0.3)@CSP48 [CX5002]  
MX26LV160TT@TSOP48 [CX1043]  
MX26LV160TX(0.4)@CSP48 [CX5002]  
MX26LV400BX(0.3)@CSP48 [CX5002]  
MX26LV400TT@TSOP48 [CX1043]  
MX26LV400TX(0.4)@CSP48 [CX5002]  
MX26LV800BT@TSOP48 [CX1043]  
MX26LV800BX(0.4)@CSP48 [CX5002]  
MX26LV800TT@TSOP48 [CX1043]  
MX26LV800TX(0.4)@CSP48 [CX5002]  
MX27C1000@PLCC32 [CX2032]  
MX27C1000@TSOP32 [CX1002]  
MX27C1000A@PLCC32 [CX2032]  
MX27C1000A@TSOP32 [CX1002]  
MX27C1001@PLCC32 [CX2032]  
MX27C1001@TSOP32 [CX1002]  
MX27C1024@PLCC44 [CX2044]  
MX27C1024@VSOP40 [CX1005]  
MX27C1024A@PLCC44 [CX2044]  
MX27C1024A@VSOP40 [CX1005]  
MX27C1024B@PLCC44 [CX2044]  
MX27C1024B@VSOP40 [CX1005]  
MX27C1610 [CX0001]  
MX27C2000@PLCC32 [CX2032]  
MX27C2000@TSOP32 [CX1002]  
MX27C2000A@PLCC32 [CX2032]  
MX27C2000A@TSOP32 [CX1002]  
MX27C2048@PLCC44 [CX2044]  
MX27C2100 [CX0001]  
MX27C256@PLCC32 [CX2032]  
MX27C4000@PLCC32 [CX2032]  
MX27C4000@TSOP32 [CX1002]  
MX27C4000A@PLCC32 [CX2032]  
MX27C4000A@TSOP32 [CX1002]  
MX27C4096@PLCC44 [CX2044]  
MX27C4111 [CX0001]  
MX27C512@PLCC32 [CX2032]  
MX27C516@PLCC44 [CX2044]  
MX27C8000 [CX0001]  
MX27C8000@SOIC32 [CX1034]

MX27C8000@TSOP32 [CX1002]  
MX27C8000A@PLCC32 [CX2032]  
MX27C8000A@TSOP32 [CX1002]  
MX27C8100@PSOP44 [CX1014]  
MX27C8111@PSOP44 [CX1014]  
MX27L1000@PLCC32 [CX2032]  
MX27L2000 [CX0001]  
MX27L2000@TSOP32 [CX1002]  
MX27L256@PLCC32 [CX2032]  
MX27L4000 [CX0001]  
MX27L4000@TSOP32 [CX1002]  
MX27L4096@PLCC44 [CX2044]  
MX27L512@PLCC32 [CX2032]  
MX28F002B@TSOP40 [CX1006]  
MX28F1000 [CX0001]  
MX28F1000(REVERSE)@TSOP32 [CX1002]  
MX28F1000@PLCC32 [CX2032]  
MX28F1000@TSOP32 [CX1002]  
MX28F1000P(REVERSE)@TSOP32 [CX1002]  
MX28F1000P@PLCC32 [CX2032]  
MX28F160C3BT@TSOP48 [CX1004]  
MX28F160C3TT@TSOP48 [CX1004]  
MX28F2000 [CX0001]  
MX28F2000(REVERSE)@TSOP32 [CX1002]  
MX28F2000@PLCC32 [CX2032]  
MX28F2000P [CX0001]  
MX28F2000P(REVERSE)@TSOP32 [CX1002]  
MX28F2000P@PLCC32 [CX2032]  
MX28F2100B@PSOP44 [CX1014]  
MX28F2100T@PSOP44 [CX1014]  
MX28F4000 [CX0001]  
MX28F4000@SOP32 [CX1019]  
MX28F640C3BT@TSOP48 [CX1004]  
MX28F640C3TT@TSOP48 [CX1004]  
MX29F001B [CX0001]  
MX29F001B@TSOP32 [CX1002]  
MX29F001T@PLCC32 [CX2032]  
MX29F002B [CX0001]  
MX29F002B@TSOP32 [CX1002]  
MX29F002NB@PLCC32 [CX2032]  
MX29F002NT [CX0001]  
MX29F002NT@TSOP32 [CX1002]  
MX29F002T@PLCC32 [CX2032]  
MX29F004B [CX0001]  
MX29F004B@TSOP32 [CX1002]  
MX29F004T@PLCC32 [CX2032]  
MX29F016(REVERSE)@TSOP40 [CX1006]  
MX29F016(REVERSE)@TSOP48 [CX1004]  
MX29F016@PSOP44 [CX1014]  
MX29F016@TSOP48 [CX1004]  
MX29F022B@PLCC32 [CX2032]  
MX29F022NB [CX0001]  
MX29F022NB@TSOP32 [CX1002]  
MX29F022NT@PLCC32 [CX2032]  
MX29F022T [CX0001]  
MX29F022T@TSOP32 [CX1002]  
MX29F040@PLCC32 [CX2032]  
MX29F040C [CX0001]  
MX29F040C@TSOP32 [CX1002]  
MX27C8000A [CX0001]  
MX27C8000A@SOIC32 [CX1034]  
MX27C8100 [CX0001]  
MX27C8111 [CX0001]  
MX27L1000 [CX0001]  
MX27L1000@TSOP32 [CX1002]  
MX27L2000@PLCC32 [CX2032]  
MX27L256 [CX0001]  
MX27L256@TSOP32 [CX1024]  
MX27L4000@PLCC32 [CX2032]  
MX27L4096 [CX0001]  
MX27L512 [CX0001]  
MX27L512@TSOP28 [CX1024]  
MX28F002T@TSOP40 [CX1006]  
MX28F1000@SOP32 [CX1019]  
MX28F1000P [CX0001]  
MX28F1000P@TSOP32 [CX1002]  
MX28F160C3BX@uBGA48 [CX50UN]  
MX28F160C3TX@uBGA48 [CX50UN]  
MX28F2000@TSOP32 [CX1002]  
MX28F2000P@TSOP32 [CX1002]  
MX28F2100B@TSOP48 [CX1004]  
MX28F2100T@TSOP48 [CX1004]  
MX28F4000@PLCC32 [CX2032]  
MX28F4000@TSOP32 [CX1002]  
MX28F640C3BX@uBGA48 [CX50UN]  
MX28F640C3TX@uBGA48 [CX50UN]  
MX29F001B@PLCC32 [CX2032]  
MX29F001T [CX0001]  
MX29F001T@TSOP32 [CX1002]  
MX29F002B@PLCC32 [CX2032]  
MX29F002NB [CX0001]  
MX29F002NB@TSOP32 [CX1002]  
MX29F002NT@PLCC32 [CX2032]  
MX29F002T [CX0001]  
MX29F002T@TSOP32 [CX1002]  
MX29F004B@PLCC32 [CX2032]  
MX29F004T [CX0001]  
MX29F004T@TSOP32 [CX1002]  
MX29F016@TSOP40 [CX1006]  
MX29F022B [CX0001]  
MX29F022B@TSOP32 [CX1002]  
MX29F022NB@PLCC32 [CX2032]  
MX29F022NT [CX0001]  
MX29F022NT@TSOP32 [CX1002]  
MX29F022T@PLCC32 [CX2032]  
MX29F040 [CX0001]  
MX29F040@TSOP32 [CX1002]  
MX29F040C@PLCC32 [CX2032]

MX29F080(REVERSE)@TSOP40 [CX1006]  
MX29F080@PSOP44 [CX1014]  
MX29F100B@PSOP44 [CX1014]  
MX29F100T@PSOP44 [CX1014]  
MX29F1610@PSOP44 [CX1014]  
MX29F1610A@PSOP44 [CX1014]  
MX29F1610B@TSOP48 [CX1004]  
MX29F1615 [CX0001]  
MX29F200B(REVERSE)@TSOP48 [CX1004]  
MX29F200B@PSOP44 [CX1014]  
MX29F200CB@PSOP44 [CX1014]  
MX29F200CT@PSOP44 [CX1014]  
MX29F200T(REVERSE)@TSOP48 [CX1004]  
MX29F200T@PSOP44 [CX1014]  
MX29F4000 [CX0001]  
MX29F400B(REVERSE)@TSOP48 [CX1004]  
MX29F400B@PSOP44 [CX1014]  
MX29F400CB@PSOP44 [CX1014]  
MX29F400CT@PSOP44 [CX1014]  
MX29F400T(REVERSE)@TSOP48 [CX1004]  
MX29F400T@PSOP44 [CX1014]  
MX29F800B(REVERSE)@TSOP48 [CX1004]  
MX29F800B@PSOP44 [CX1014]  
MX29F800CBM@PSOP44 [CX1014]  
MX29F800CBXB@FBGA48 [CX5002]  
MX29F800CTT@TSOP48 [CX1043]  
MX29F800T(REVERSE)@TSOP48 [CX1004]  
MX29F800T@PSOP44 [CX1014]  
MX29F8100@PSOP44 [CX1014]  
MX29GA128EHXC@FBGA64 [CX5004]  
MX29GA128ELXC@FBGA64 [CX5004]  
MX29GA129EHXC@FBGA64 [CX5004]  
MX29GA129ELXC@FBGA64 [CX5004]  
MX29GA256EHXC@FBGA64 [CX5004]  
MX29GA256ELXC@FBGA64 [CX5004]  
MX29GA256FHXF@FBGA64 [CX5074]  
MX29GA257EHXC@FBGA64 [CX5004]  
MX29GA257ELXC@FBGA64 [CX5004]  
MX29GA257FHXC@FBGA64 [CX5004]  
MX29GA320EHXF@FBGA64 [CX5074]  
MX29GA321EHXC@FBGA64 [CX5004]  
MX29GA512FHXF@FBGA64 [CX5074]  
MX29GA640EHXF@FBGA64 [CX5074]  
MX29GA641EHXC@FBGA64 [CX5004]  
MX29GL128EDT2@TSOP56 [CX1011]  
MX29GL128EHT2@TSOP56 [CX1011]  
MX29GL128EHXF@FBGA64 [CX5074]  
MX29GL128ELXC@FBGA64 [CX5004]  
MX29GL128EUT2@TSOP56 [CX1011]  
MX29GL128FDT2@TSOP56 [CX1011]  
MX29GL128FDXG@FBGA56 [CX5045]  
MX29GL128FHXF@FBGA64 [CX5074]  
MX29GL128FLT2@TSOP56 [CX1011]  
MX29GL128FLXG@FBGA56 [CX5045]  
MX29GL128FUXF@FBGA64 [CX5074]  
MX29GL256EDT2@TSOP56 [CX1011]  
MX29GL256EHT2@TSOP56 [CX1011]  
MX29GL256EHXF@FBGA64 [CX5074]  
MX29GL256ELXC@FBGA64 [CX5004]  
MX29F080@TSOP40 [CX1006]  
MX29F100B@TSOP48 [CX1004]  
MX29F100T@TSOP48 [CX1004]  
MX29F1610@TSOP48 [CX1004]  
MX29F1610A@TSOP48 [CX1004]  
MX29F1611@PSOP44 [CX1014]  
MX29F200B@TSOP48 [CX1004]  
MX29F200CB@TSOP48 [CX1043]  
MX29F200CT@TSOP48 [CX1043]  
MX29F200T@TSOP48 [CX1004]  
MX29F400B@TSOP48 [CX1004]  
MX29F400CB@TSOP48 [CX1043]  
MX29F400CT@TSOP48 [CX1043]  
MX29F400T@TSOP48 [CX1004]  
MX29F800B@TSOP48 [CX1004]  
MX29F800CBT@TSOP48 [CX1043]  
MX29F800CTM@PSOP44 [CX1014]  
MX29F800CTXB@FBGA48 [CX5002]  
MX29F800T@TSOP48 [CX1004]  
MX29F8100@TSOP48 [CX1004]  
MX29GA128EHXF@FBGA64 [CX5074]  
MX29GA128ELXF@FBGA64 [CX5074]  
MX29GA129EHXF@FBGA64 [CX5074]  
MX29GA129ELXF@FBGA64 [CX5074]  
MX29GA256EHXF@FBGA64 [CX5074]  
MX29GA256ELXF@FBGA64 [CX5074]  
MX29GA256FLXF@FBGA64 [CX5074]  
MX29GA257EHXF@FBGA64 [CX5074]  
MX29GA257ELXF@FBGA64 [CX5074]  
MX29GA257FLXC@FBGA64 [CX5004]  
MX29GA320ELXF@FBGA64 [CX5074]  
MX29GA321ELXC@FBGA64 [CX5004]  
MX29GA512FLXF@FBGA64 [CX5074]  
MX29GA640ELXF@FBGA64 [CX5074]  
MX29GA641ELXC@FBGA64 [CX5004]  
MX29GL128EDXF@FBGA64 [CX5074]  
MX29GL128EHXC@FBGA64 [CX5004]  
MX29GL128ELT2@TSOP56 [CX1011]  
MX29GL128ELXF@FBGA64 [CX5074]  
MX29GL128EUXF@FBGA64 [CX5074]  
MX29GL128FDXF@FBGA64 [CX5074]  
MX29GL128FHT2@TSOP56 [CX1011]  
MX29GL128FHXG@FBGA56 [CX5045]  
MX29GL128FLXF@FBGA64 [CX5074]  
MX29GL128FUT2@TSOP56 [CX1011]  
MX29GL128FUXG@FBGA56 [CX5045]  
MX29GL256EDXF@FBGA64 [CX5074]  
MX29GL256EHXC@FBGA64 [CX5004]  
MX29GL256ELT2@TSOP56 [CX1011]  
MX29GL256ELXF@FBGA64 [CX5074]

MX29GL256ES@SSOP56 [CX1057]  
MX29GL256EUXF@FBGA64 [CX5074]  
MX29GL256FDXF@FBGA64 [CX5074]  
MX29GL256FHT2@TSOP56 [CX1011]  
MX29GL256FHXG@FBGA56 [CX5045]  
MX29GL256FLXF@FBGA64 [CX5074]  
MX29GL256FUT2@TSOP56 [CX1011]  
MX29GL256FUXG@FBGA56 [CX5045]  
MX29GL320EBXE@FBGA48 [CX5002]  
MX29GL320EHXF@FBGA64 [CX5074]  
MX29GL320ELXF@FBGA64 [CX5074]  
MX29GL320ETXE@FBGA48 [CX5002]  
MX29GL512EHXF@FBGA64 [CX5074]  
MX29GL512ELXF@FBGA64 [CX5074]  
MX29GL512FDXF@FBGA64 [CX5074]  
MX29GL512FHXF@FBGA64 [CX5074]  
MX29GL512FLXF@FBGA64 [CX5074]  
MX29GL512FUXF@FBGA64 [CX5074]  
MX29GL640EBXE@FBGA48 [CX5002]  
MX29GL640EHXF@FBGA64 [CX5074]  
MX29GL640ELXF@FBGA64 [CX5074]  
MX29GL640ETXE@FBGA48 [CX5002]  
MX29L1611@PSOP44 [CX1014]  
MX29L3211@PSOP44 [CX1014]  
MX29L8100B@TSOP48 [CX1004]  
MX29L8100T@TSOP48 [CX1004]  
MX29LA128DT@FBGA64 [CX5004]  
MX29LA128MT@TSOP56 [CX1011]  
MX29LA129DT@FBGA64 [CX5004]  
MX29LA129ML@TSOP56 [CX1011]  
MX29LA320DL@FBGA64 [CX5004]  
MX29LA320MB@TSOP48 [CX1004]  
MX29LA320MT@TSOP48 [CX1004]  
MX29LA321DL@FBGA64 [CX5004]  
MX29LA321MB@TSOP56 [CX1011]  
MX29LA321MH@TSOP56 [CX1011]  
MX29LA321ML@TSOP56 [CX1011]  
MX29LA321MT@TSOP56 [CX1011]  
MX29LA640EL@FBGA64 [CX5004]  
MX29LA641DL@FBGA64 [CX5004]  
MX29LV002CB@TSOP32 [CX1002]  
MX29LV002CT@TSOP32 [CX1002]  
MX29LV002NCB@TSOP32 [CX1002]  
MX29LV002NCT@TSOP32 [CX1002]  
MX29LV004B@TSOP40 [CX1006]  
MX29LV004CB@TSOP40 [CX1006]  
MX29LV004CT@TSOP40 [CX1006]  
MX29LV004T@TSOP40 [CX1006]  
MX29LV008BB@TSOP40 [CX1006]  
MX29LV008CB@TSOP40 [CX1006]  
MX29LV008T@TSOP40 [CX1006]  
MX29LV017AX@FBGA48 [CX5002]  
MX29LV017BX@FBGA48 [CX5002]  
MX29LV033M@TSOP40 [CX1006]  
MX29LV040@PLCC32 [CX2032]  
MX29LV040C@PLCC32 [CX2032]  
MX29LV065BT@TSOP48 [CX1004]  
MX29LV065M@TSOP48 [CX1004]  
MX29LV128DB@TSOP48 [CX1004]

MX29GL256EUT2@TSOP56 [CX1011]  
MX29GL256FDT2@TSOP56 [CX1011]  
MX29GL256FDXG@FBGA56 [CX5045]  
MX29GL256FHXF@FBGA64 [CX5074]  
MX29GL256FLT2@TSOP56 [CX1011]  
MX29GL256FLXG@FBGA56 [CX5045]  
MX29GL256FUXF@FBGA64 [CX5074]  
MX29GL320EB@TSOP48 [CX1004]  
MX29GL320EHT2@TSOP56 [CX1011]  
MX29GL320ELT2@TSOP56 [CX1011]  
MX29GL320ET@TSOP48 [CX1004]  
MX29GL512EHT2@TSOP56 [CX1011]  
MX29GL512ELT2@TSOP56 [CX1011]  
MX29GL512FDT2@TSOP56 [CX1011]  
MX29GL512FHT2@TSOP56 [CX1011]  
MX29GL512FLT2@TSOP56 [CX1011]  
MX29GL512FUT2@TSOP56 [CX1011]  
MX29GL640EB@TSOP48 [CX1004]  
MX29GL640EHT2@TSOP56 [CX1011]  
MX29GL640ELT2@TSOP56 [CX1011]  
MX29GL640ET@TSOP48 [CX1004]  
MX29L1611 [CX0001]  
MX29L1611@TSOP48 [CX1004]  
MX29L3211@TSOP48 [CX1004]  
MX29L8100G [CX0001]  
MX29LA128DB@FBGA64 [CX5004]  
MX29LA128MB@TSOP56 [CX1011]  
MX29LA129DB@FBGA64 [CX5004]  
MX29LA129MH@TSOP56 [CX1011]  
MX29LA320DH@FBGA64 [CX5004]  
MX29LA320MB@CFBGA48 [CX5002]  
MX29LA320MT@CFBGA48 [CX5002]  
MX29LA321DH@FBGA64 [CX5004]  
MX29LA321MB@FBGA64 [CX5004]  
MX29LA321MH@FBGA64 [CX5004]  
MX29LA321ML@FBGA64 [CX5004]  
MX29LA321MT@FBGA64 [CX5004]  
MX29LA640EH@FBGA64 [CX5004]  
MX29LA641DH@FBGA64 [CX5004]  
MX29LV002CB@PLCC32 [CX2032]  
MX29LV002CT@PLCC32 [CX2032]  
MX29LV002NCB@PLCC32 [CX2032]  
MX29LV002NCT@PLCC32 [CX2032]  
MX29LV004B@PLCC32 [CX2032]  
MX29LV004CB@PLCC32 [CX2032]  
MX29LV004CT@PLCC32 [CX2032]  
MX29LV004T@PLCC32 [CX2032]  
MX29LV008B@TSOP40 [CX1006]  
MX29LV008BT@TSOP40 [CX1006]  
MX29LV008CT@TSOP40 [CX1006]  
MX29LV017AT@TSOP40 [CX1006]  
MX29LV017BT@TSOP40 [CX1006]  
MX29LV033AT@TSOP40 [CX1006]  
MX29LV033T@TSOP40 [CX1006]  
MX29LV040@TSOP32 [CX1002]  
MX29LV040C@TSOP32 [CX1002]  
MX29LV065BXB@FBGA63 [CX5041]  
MX29LV081@TSOP40 [CX1006]  
MX29LV128DB@TSOP56 [CX1011]

MX29LV128DT@TSOP48 [CX1004]  
MX29LV128MB@TSOP56 [CX1011]  
MX29LV128ML@TSOP56 [CX1011]  
MX29LV160AB(0.3)@CSP48 [CX5002]  
MX29LV160AB@PSOP44 [CX1014]  
MX29LV160AT(0.3)@CSP48 [CX5002]  
MX29LV160AT@PSOP44 [CX1014]  
MX29LV160B(0.3)@CSP48 [CX5002]  
MX29LV160B@PSOP44 [CX1014]  
MX29LV160BB(0.3)@CSP48 [CX5002]  
MX29LV160BB@PSOP44 [CX1014]  
MX29LV160BT(0.3)@CSP48 [CX5002]  
MX29LV160BT@PSOP44 [CX1014]  
MX29LV160CBM@PSOP44 [CX1014]  
MX29LV160CBXB(0.3)@CSP48 [CX5002]  
MX29LV160CBXE(0.4)@CSP48 [CX5002]  
MX29LV160CTM@PSOP44 [CX1014]  
MX29LV160CTXB(0.3)@CSP48 [CX5002]  
MX29LV160CTXE(0.4)@CSP48 [CX5002]  
MX29LV160DBGB@WFLGA48 [CX5037]  
MX29LV160DBXB@CSP48 [CX5002]  
MX29LV160DBXH@WFBGA48 [CX5037]  
MX29LV160DTT@TSOP48 [CX1004]  
MX29LV160DTXE@CSP48 [CX5002]  
MX29LV160T(0.3)@CSP48 [CX5002]  
MX29LV160T@PSOP44 [CX1014]  
MX29LV161DBGB@WFLGA48 [CX5037]  
MX29LV161DBXB@CSP48 [CX5002]  
MX29LV161DTGB@WFLGA48 [CX5037]  
MX29LV161DTXB@CSP48 [CX5002]  
MX29LV320ABT@TSOP48 [CX1004]  
MX29LV320ABXE@CSP48 [CX5002]  
MX29LV320ATXB@CSP48 [CX5002]  
MX29LV320BT@TSOP48 [CX1004]  
MX29LV320BXE@CSP48 [CX5002]  
MX29LV320CBXB@CSP48 [CX5002]  
MX29LV320CTT@TSOP48 [CX1004]  
MX29LV320CTXE@CSP48 [CX5002]  
MX29LV320DBXB@CSP48 [CX5002]  
MX29LV320DTT@TSOP48 [CX1004]  
MX29LV320DTXE@CSP48 [CX5002]  
MX29LV320EBE@CSP48 [CX5002]  
MX29LV320ETB@CSP48 [CX5002]  
MX29LV320ETT@TSOP48 [CX1004]  
MX29LV320MB@PSOP44 [CX1014]  
MX29LV320MH@TSOP56 [CX1011]  
MX29LV320MT@CFBGA48 [CX5002]  
MX29LV320MT@TSOP48 [CX1004]  
MX29LV320TXB@CSP48 [CX5002]  
MX29LV321DBT@TSOP48 [CX1004]  
MX29LV321DTT@TSOP48 [CX1004]  
MX29LV400B@PSOP44 [CX1014]  
MX29LV400BX(0.3)@CSP48 [CX5002]  
MX29LV400CBM@PSOP44 [CX1014]  
MX29LV400CBXB(0.3)@CSP48 [CX5002]  
MX29LV400CBXE(0.4)@CSP48 [CX5002]  
MX29LV400CTM@PSOP44 [CX1014]  
MX29LV400CTXB(0.3)@CSP48 [CX5002]  
MX29LV400CTXE(0.4)@CSP48 [CX5002]

MX29LV128DT@TSOP56 [CX1011]  
MX29LV128MH@TSOP56 [CX1011]  
MX29LV128MT@TSOP56 [CX1011]  
MX29LV160AB(0.4)@CSP48 [CX5002]  
MX29LV160AB@TSOP48 [CX1004]  
MX29LV160AT(0.4)@CSP48 [CX5002]  
MX29LV160AT@TSOP48 [CX1004]  
MX29LV160B(0.4)@CSP48 [CX5002]  
MX29LV160B@TSOP48 [CX1004]  
MX29LV160BB(0.4)@CSP48 [CX5002]  
MX29LV160BB@TSOP48 [CX1004]  
MX29LV160BT(0.4)@CSP48 [CX5002]  
MX29LV160BT@TSOP48 [CX1004]  
MX29LV160CBT@TSOP48 [CX1004]  
  
MX29LV160CTT@TSOP48 [CX1004]  
  
MX29LV160DBT@TSOP48 [CX1004]  
MX29LV160DBXE@CSP48 [CX5002]  
MX29LV160DTGB@WFLGA48 [CX5037]  
MX29LV160DTXB@CSP48 [CX5002]  
MX29LV160DTXH@WFBGA48 [CX5037]  
MX29LV160T(0.4)@CSP48 [CX5002]  
MX29LV160T@TSOP48 [CX1004]  
MX29LV161DBT@TSOP48 [CX1004]  
MX29LV161DBXH@WFBGA48 [CX5037]  
MX29LV161DTT@TSOP48 [CX1004]  
MX29LV161DTXH@WFBGA48 [CX5037]  
MX29LV320ABXB@CSP48 [CX5002]  
MX29LV320ATT@TSOP48 [CX1004]  
MX29LV320ATXE@CSP48 [CX5002]  
MX29LV320BXB@CSP48 [CX5002]  
MX29LV320CBT@TSOP48 [CX1004]  
MX29LV320CBXE@CSP48 [CX5002]  
MX29LV320CTXB@CSP48 [CX5002]  
MX29LV320DBT@TSOP48 [CX1004]  
MX29LV320DBXE@CSP48 [CX5002]  
MX29LV320DTXB@CSP48 [CX5002]  
MX29LV320EBB@CSP48 [CX5002]  
MX29LV320EBT@TSOP48 [CX1004]  
MX29LV320ETE@CSP48 [CX5002]  
MX29LV320MB@CFBGA48 [CX5002]  
MX29LV320MB@TSOP48 [CX1004]  
MX29LV320ML@TSOP56 [CX1011]  
MX29LV320MT@PSOP44 [CX1014]  
MX29LV320TT@TSOP48 [CX1004]  
MX29LV320TXE@CSP48 [CX5002]  
MX29LV321DBXB@CSP48 [CX5002]  
MX29LV321DTXB@FBGA48 [CX5002]  
MX29LV400B@TSOP48 [CX1004]  
MX29LV400BX(0.4)@CSP48 [CX5002]  
MX29LV400CBT@TSOP48 [CX1004]  
  
MX29LV400CTT@TSOP48 [CX1004]



MX29LV400T@PSOP44 [CX1014]  
MX29LV400TX(0.3)@CSP48 [CX5002]  
MX29LV640BBT@TSOP48 [CX1004]  
MX29LV640BT@TSOP48 [CX1004]  
MX29LV640BTXB@FBGA63 [CX5041]  
MX29LV640BUXB@FBGA63 [CX5041]  
MX29LV640BXC@FBGA64 [CX5004]  
MX29LV640DBT@TSOP48 [CX1004]  
MX29LV640DTM@PSOP44 [CX1014]  
MX29LV640DTX@FBGA48 [CX5002]  
MX29LV640EBX@FBGA48 [CX5002]  
MX29LV640ETX@FBGA48 [CX5002]  
MX29LV640MB@TSOP48 [CX1004]  
MX29LV640MH@TSOP56 [CX1011]  
MX29LV640ML@TSOP56 [CX1011]  
MX29LV640MT@TSOP48 [CX1004]  
MX29LV640TT@TSOP48 [CX1004]  
MX29LV640TXC@FBGA64 [CX5004]  
MX29LV640UXB@FBGA63 [CX5041]  
MX29LV641MH@TSOP48 [CX1004]  
MX29LV800AB(0.3)@CSP48 [CX5002]  
MX29LV800AB@PSOP44 [CX1014]  
MX29LV800AT(0.3)@CSP48 [CX5002]  
MX29LV800AT@PSOP44 [CX1014]  
MX29LV800B(0.3)@CSP48 [CX5002]  
MX29LV800B@PSOP44 [CX1014]  
MX29LV800CBM@PSOP44 [CX1014]  
MX29LV800CBXB(0.3)@CSP48 [CX5002]  
MX29LV800CBXE(0.4)@CSP48 [CX5002]  
MX29LV800CTM@PSOP44 [CX1014]  
MX29LV800CTXB(0.3)@CSP48 [CX5002]  
MX29LV800CTXE(0.4)@CSP48 [CX5002]  
MX29LV800T(0.3)@CSP48 [CX5002]  
MX29LV800T@PSOP44 [CX1014]  
MX29LW160BT@TSOP48 [CX1004]  
MX29LW160BXA(0.75)@CSP48 [CX50UN]  
MX29LW160BXB(0.80)@CSP48 [CX5022]  
MX29LW160TT@TSOP48 [CX1004]  
MX29LW160TXA(0.75)@CSP48 [CX50UN]  
MX29LW160TXB(0.80)@CSP48 [CX5005]  
MX29LW161BT@TSOP48 [CX1004]  
MX29LW161BXA(0.75)@CSP48 [CX50UN]  
MX29LW161BXB(0.80)@CSP48 [CX5022]  
MX29LW161TT@TSOP48 [CX1004]  
MX29LW161TXA(0.75)@CSP48 [CX50UN]  
MX29LW161TXB(0.80)@CSP48 [CX5022]  
MX29LW320BT@TSOP48 [CX1004]  
MX29LW320BXA(0.75)@CSP48 [CX50UN]  
MX29LW320BXB(0.80)@CSP48 [CX5005]  
MX29LW320TT@TSOP48 [CX1004]  
MX29LW320TXA(0.75)@CSP48 [CX50UN]  
MX29LW320TXB(0.80)@CSP48 [CX5005]  
MX29LW321BT@TSOP48 [CX1004]  
MX29LW321BXA(0.75)@CSP48 [CX50UN]  
MX29LW321BXB(0.80)@CSP48 [CX5005]  
MX29LW321TT@TSOP48 [CX1004]  
MX29LW321TXA(0.75)@CSP48 [CX50UN]  
MX29LW321TXB(0.80)@CSP48 [CX5005]  
MX29NS128EXJ1@FBGA56 [CX5094]

MX29LV400T@TSOP48 [CX1004]  
MX29LV400TX(0.4)@CSP48 [CX5002]  
MX29LV640BBXB@FBGA63 [CX5041]  
MX29LV640BTT@TSOP48 [CX1004]  
MX29LV640BUT@TSOP48 [CX1004]  
MX29LV640BXB@FBGA63 [CX5041]  
MX29LV640DBM@PSOP44 [CX1014]  
MX29LV640DBX@FBGA48 [CX5002]  
MX29LV640DTT@TSOP48 [CX1004]  
MX29LV640EBT@TSOP48 [CX1004]  
MX29LV640ETT@TSOP48 [CX1004]  
MX29LV640MB@FBGA63 [CX5041]  
MX29LV640MH@FBGA64 [CX5004]  
MX29LV640ML@FBGA64 [CX5004]  
MX29LV640MT@FBGA63 [CX5041]  
MX29LV640MU@FBGA63 [CX5041]  
MX29LV640TXB@FBGA63 [CX5041]  
MX29LV640UT@TSOP48 [CX1004]  
MX29LV640UXC@FBGA64 [CX5004]  
MX29LV641ML@TSOP48 [CX1004]  
MX29LV800AB(0.4)@CSP48 [CX5002]  
MX29LV800AB@TSOP48 [CX1004]  
MX29LV800AT(0.4)@CSP48 [CX5002]  
MX29LV800AT@TSOP48 [CX1004]  
MX29LV800B(0.4)@CSP48 [CX5002]  
MX29LV800B@TSOP48 [CX1004]  
MX29LV800CBT@TSOP48 [CX1004]  
  
MX29LV800CTT@TSOP48 [CX1004]  
  
MX29LV800T(0.4)@CSP48 [CX5002]  
MX29LV800T@TSOP48 [CX1004]  
  
MX29NS320EXJ1@FBGA56 [CX5094]

MX29NS640EXJ1@FBGA56 [CX5094]  
MX29SL402CBT@TSOP48 [CX1004]  
MX29SL402CBXE@CSP48 [CX5002]  
MX29SL402CTGB@WFLGA48 [CX5037]  
MX29SL402CTXB@CSP48 [CX5002]  
MX29SL402CTXH@WFBGA48 [CX5037]  
MX29SL800CBXB(0.30)@CSP48 [CX5002]  
MX29SL800CBXE(0.40)@CSP48 [CX5002]  
MX29SL800CBXH(0.30)@CSP48 [CX5038]  
MX29SL800CT@TSOP48 [CX1004]  
MX29SL800CTXB(0.30)@CSP48 [CX5002]  
MX29SL800CTXE(0.40)@CSP48 [CX5002]  
MX29SL800CTXH(0.30)@CSP48 [CX5038]  
MX29SL802CBGB@WFLGA48 [CX5037]  
MX29SL802CBXB@CSP48 [CX5002]  
MX29SL802CBXH@WFBGA48 [CX5037]  
MX29SL802CTT@TSOP48 [CX1004]  
MX29SL802CTXE@CSP48 [CX5002]  
MX66L51235F@SOP16 [CX1033#1]  
MX66L51235F@WSON8 [CX4006#1]  
MX68GA1G0FLXF@FBGA64 [CX5074]  
MX68GL1G0FDXF@FBGA64 [CX5074]  
MX68GL1G0FHXF@FBGA64 [CX5074]  
MX68GL1G0FLXF@FBGA64 [CX5074]  
MX68GL1G0FUXF@FBGA64 [CX5074]  
MX69F1602C3TX@FBGA72 [CX5001]  
MX69F1604C3TX@FBGA72 [CX5001]  
MX69F3204C3TX@FBGA72 [CX5026]  
MX69GL127EBXGW@FBGA56 [CX5045]  
MX69GL128EAXGW@FBGA64 [CX5001]  
MX69GL128ECXGW@FBGA64 [CX5001]  
MX69GL638EJXGI@FBGA56 [CX5045]  
MX69GL640EAXGW@FBGA56 [CX5045]  
MX69GL640ECXGW@FBGA56 [CX5045]  
MX69GL642EAXGI@FBGA56 [CX5045]  
MX69LW162BXB@CSP69 [CX5001]  
MX69LW164BXB@CSP69 [CX5001]  
MX69LW322BXB@CSP69 [CX5001]  
MX69LW324BXB@CSP69 [CX5001]  
MX69N28E32AXJW@FBGA56 [CX5094]  
MX69N28E32FXJW@FBGA56 [CX5094]  
MX69N28E64FXJW@FBGA56 [CX5094]  
MX69N64E32BXJW@FBGA56 [CX5094]  
MX29SL402CBGB@WFLGA48 [CX5037]  
MX29SL402CBXB@CSP48 [CX5002]  
MX29SL402CBXH@WFBGA48 [CX5037]  
MX29SL402CTT@TSOP48 [CX1004]  
MX29SL402CTXE@CSP48 [CX5002]  
MX29SL800CB@TSOP48 [CX1004]  
MX29SL802CBT@TSOP48 [CX1004]  
MX29SL802CBXE@CSP48 [CX5002]  
MX29SL802CTGB@WFLGA48 [CX5037]  
MX29SL802CTXB@CSP48 [CX5002]  
MX29SL802CTXH@WFBGA48 [CX5037]  
MX66L51235F@TFBGA24 [CX5157]  
MX68GA1G0FHXF@FBGA64 [CX5074]  
MX68GL1G0FDT2@TSOP56 [CX1011]  
MX68GL1G0FHT2@TSOP56 [CX1011]  
MX68GL1G0FLT2@TSOP56 [CX1011]  
MX68GL1G0FUT2@TSOP56 [CX1011]  
MX69F1602C3BX@FBGA72 [CX5001]  
MX69F1604C3BX@FBGA72 [CX5001]  
MX69F3204C3BX@FBGA72 [CX5026]  
MX69GL127EAXGW@FBGA56 [CX5045]  
MX69GL127ECXGW@FBGA56 [CX5045]  
MX69GL128EBXGW@FBGA64 [CX5001]  
MX69GL638EAXGI@FBGA56 [CX5045]  
MX69GL640EAXGI@FBGA56 [CX5045]  
MX69GL640EBXGW@FBGA56 [CX5045]  
MX69GL640EJXGI@FBGA56 [CX5045]  
MX69GL642EJXGI@FBGA56 [CX5045]  
MX69LW162TXB@CSP69 [CX5001]  
MX69LW164TXB@CSP69 [CX5001]  
MX69LW322TXB@CSP69 [CX5001]  
MX69LW324TXB@CSP69 [CX5001]  
MX69N28E32BXJW@FBGA56 [CX5094]  
MX69N28E64AXJW@FBGA56 [CX5094]  
MX69N64E32AXJW@FBGA56 [CX5094]  
MX69N64E32FXJW@FBGA56 [CX5094]

## MICROCONTROLLER

MX10E8050I [CX0001]  
MX10E8050I@TQFP44 [CX3003]  
MX10EXAU@TQFP44 [CX3003]  
MX10FMAXD [CX0001]  
MX10FMAXD@TQFP44 [CX3002]  
MX10E8050I@PLCC44 [CX2044]  
MX10EXAQ@PLCC44 [CX2044]  
MX10FLCD [CX0001]  
MX10FMAXD@PLCC44 [CX2044]

## MAGNACHIP

## MICROCONTROLLER

GMS34004TK [CX0001]  
GMS34004TM [CX0001]

GMS34004TW [CX0001]  
GMS34112TK@SOIC20 [CX1033]  
GMS34140TK [CX0001]  
GMS81504AT [CX0032]  
GMS81604T [CX0001]  
GMS81604T@SDIP42 [CX0042]  
GMS81608T@PLCC44 [CX2044]  
GMS87C1102 [CX0001]  
GMS87C1202 [CX0001]  
GMS87C1404 [CX0001]  
GMS87C1408 [CX0001]  
GMS97C1051 [CX0001]  
GMS97C2051 [CX0001]  
GMS97C51 [CX0001]  
GMS97C51@TQFP44 [CX3002]  
GMS97C51H@PLCC44 [CX2044]  
GMS97C52 [CX0001]  
GMS97C52@TQFP44 [CX3002]  
GMS97C52H@PLCC44 [CX2044]  
GMS97C54 [CX0001]  
GMS97C54@TQFP44 [CX3002]  
GMS97C54H@PLCC44 [CX2044]  
GMS97C56 [CX0001]  
GMS97C56@TQFP44 [CX3002]  
GMS97C56H@PLCC44 [CX2044]  
GMS97C58 [CX0001]  
GMS97C58@TQFP44 [CX3002]  
GMS97C58H@PLCC44 [CX2044]  
GMS97L1051 [CX0001]  
GMS97L2051 [CX0001]  
GMS97L51 [CX0001]  
GMS97L51@TQFP44 [CX3002]  
GMS97L52@PLCC44 [CX2044]  
GMS97L54 [CX0001]  
GMS97L54@TQFP44 [CX3002]  
GMS97L56@PLCC44 [CX2044]  
GMS97L58 [CX0001]  
GMS97L58@TQFP44 [CX3002]  
HMS87C1404B@SDIP28 [CX0032]  
HMS87C1408B [CX0001]  
HMS87C1408B@SOIC28 [CX1033]  
HMS87C1416B@SDIP28 [CX0032]  
HMS87C1508B [CX0001]  
HMS87C1608B [CX0001]  
HMS87C1708B@SDIP42 [CX0042]  
HMS87C1808B@TQFP44 [CX3002]  
HMS87C5216 [CX0001]  
HMS87C5216@SOIC28 [CX1033]  
MC80F0504 [CX0001]  
MC80F0504@SSOP16 [CX1026]  
MC80F0604 [CX0001]  
MC80F0604@SSOP20 [CX1026]  
MC80F0704@QFN28 [CX0001]  
MC80F0708 [CX0001]  
MC80F0708@SOP28 [CX1036]  
MC80F0804@SOP32 [CX1069]  
MC80F0808@SOP32 [CX1069]

GMS34112TK [CX0001]  
GMS34112TK@SSOP20 [CX1026]  
GMS34140TK@SOIC24 [CX1033]  
GMS81504T [CX0032]  
GMS81604T@PLCC44 [CX2044]  
GMS81608T [CX0001]  
GMS81608T@SDIP42 [CX0042]  
GMS87C1102@SOP16 [CX1033]  
GMS87C1202@SOP20 [CX1033]  
GMS87C1404@SOP28 [CX1033]  
GMS87C1408@SOP28 [CX1033]  
GMS97C1051@SOIC20 [CX1033]  
GMS97C2051@SOIC20 [CX1033]  
GMS97C51@PLCC44 [CX2044]  
GMS97C51H [CX0001]  
GMS97C51H@TQFP44 [CX3002]  
GMS97C52@PLCC44 [CX2044]  
GMS97C52H [CX0001]  
GMS97C52H@TQFP44 [CX3002]  
GMS97C54@PLCC44 [CX2044]  
GMS97C54H [CX0001]  
GMS97C54H@TQFP44 [CX3002]  
GMS97C56@PLCC44 [CX2044]  
GMS97C56H [CX0001]  
GMS97C56H@TQFP44 [CX3002]  
GMS97C58@PLCC44 [CX2044]  
GMS97C58H [CX0001]  
GMS97C58H@TQFP44 [CX3002]  
GMS97L1051@SOIC20 [CX1033]  
GMS97L2051@SOIC20 [CX1033]  
GMS97L51@PLCC44 [CX2044]  
GMS97L52 [CX0001]  
GMS97L52@TQFP44 [CX3002]  
GMS97L54@PLCC44 [CX2044]  
GMS97L56 [CX0001]  
GMS97L56@TQFP44 [CX3002]  
GMS97L58@PLCC44 [CX2044]  
HMS87C1404B [CX0001]  
HMS87C1404B@SOIC28 [CX1033]  
HMS87C1408B@SDIP28 [CX0032]  
HMS87C1416B [CX0001]  
HMS87C1416B@SOIC28 [CX1033]  
HMS87C1516B [CX0001]  
HMS87C1616B [CX0001]  
HMS87C1716B@SDIP42 [CX0042]  
HMS87C1816B@TQFP44 [CX3002]  
HMS87C5216@PLCC44 [CX2044]  
HMS87C5216@TQFP44 [CX3002]  
MC80F0504@SOP16 [CX1036]  
MC80F0504[153mil]@SOP16 [CX1030]  
MC80F0604@SOP20 [CX1036]  
MC80F0704 [CX0001]  
MC80F0704@SOP28 [CX1036]  
MC80F0708@QFN28 [CX0001]  
MC80F0804@SDIP32 [CX0032]  
MC80F0808@SDIP32 [CX0032]

# MAXCOM

## E (E) PROM/FRAM/NVRAM

MAX24A02 [CX0001]	MAX24A02@SOP8 [CX1045]
MAX24A02@TSSOP8 [CX1059]	MAX24A04 [CX0001]
MAX24A04@SOP8 [CX1045]	MAX24A04@TSSOP8 [CX1059]
MAX24A08 [CX0001]	MAX24A08@SOP8 [CX1045]
MAX24A08@TSSOP8 [CX1059]	MAX24A16 [CX0001]
MAX24A16@SOP8 [CX1045]	MAX24A16@TSSOP8 [CX1059]

# MAXIM

## E (E) PROM/FRAM/NVRAM

DS1220AB [CX0001]	DS1220AD [CX0001]
DS1220Y [CX0001]	DS1225AB [CX0001]
DS1225AD [CX0001]	DS1225D [CX0001]
DS1225E [CX0001]	DS1225Y [CX0001]
DS1230AB [CX0001]	DS1230W [CX0001]
DS1230Y [CX0001]	DS1235AB [CX0001]
DS1235Y [CX0001]	DS1243Y [CX0001]
DS1244 [CX0001]	DS1244P [CX2068]
DS1244Y [CX0001]	DS1244YP [CX2068]
DS1245AB [CX0001]	DS1245EE [CX0001]
DS1245P [CX2068]	DS1245W [CX0001]
DS1245Y [CX0001]	DS1248P [CX2068]
DS1248W [CX0001]	DS1248Y [CX0001]
DS1249AB [CX0001]	DS1249W [CX0001]
DS1249Y [CX0001]	DS1250AB [CX0001]
DS1250W [CX0001]	DS1250Y [CX0001]
DS1251AB [CX0001]	DS1251W [CX0001]
DS1251Y [CX0001]	DS1256P [CX2068]
DS1256W [CX0001]	DS1256Y [CX0001]
DS1258AB [CX0001]	DS1258W [CX0001]
DS1258Y [CX0001]	DS1265AB [CX0001]
DS1265W [CX0001]	DS1265Y [CX0001]
DS1270AB [CX0001]	DS1270W [CX0001]
DS1270Y [CX0001]	DS1284 [CX0001]
DS1284N [CX0001]	DS1284Q@PLCC28 [CX2028]
DS1284QN@PLCC28 [CX2028]	DS1286 [CX0001]
DS1286I [CX0001]	DS1287 [CX0001]
DS1287A [CX0001]	DS12887 [CX0001]
DS12887A [CX0001]	DS12C887 [CX0001]
DS12C887A [CX0001]	DS1386(32K) [CX0001]
DS1386(8K) [CX0001]	DS1485 [CX0001]
DS1485@SOIC28 [CX1035]	DS1488 [CX0001]
DS1501 [CX0001]	DS1511 [CX0001]
DS1553 [CX0001]	DS1553P [CX2068]
DS1553W [CX0001]	DS1553WP [CX2068]
DS1554 [CX0001]	DS1554W [CX0001]
DS1556 [CX0001]	DS1642 [CX0001]
DS1643 [CX0001]	DS1644 [CX0001]
DS1644P [CX2068]	DS1644PS [CX2068]
DS1645AB [CX0001]	DS1645EE [CX0001]
DS1645Y [CX0001]	DS1646 [CX0001]
DS1646P [CX2068]	DS1647 [CX0001]
DS1647LPM [CX2068]	DS1650AB [CX0001]

DS1650Y [CX0001]  
DS1685-3@SOP24 [CX1033]  
DS1685-5@SOP24 [CX1033]  
DS1687-5 [CX0001]  
DS17287-5 [CX0001]  
DS1742W [CX0001]  
DS1743P [CX2068]  
DS1743WP [CX2068]  
DS1744P [CX2068]  
DS1744WP [CX2068]  
DS1746P [CX2068]  
DS1747P [CX2068]  
DS1747W [CX0001]  
DS1747WPS [CX2068]  
DS17487-5 [CX0001]  
DS17887-5 [CX0001]  
DS2430AP@TSOC6 [CX1066]  
DS2431P@TSOC6 [CX1066]  
DS2433@PR-35 [CX0001]  
DS2433S(5.5)@SOIC8 [CX1044]  
DS2502P@TSOC6 [CX1066]  
DS2502UNW [CX0001]  
DS2502UNW@SOT-23 [CX1041]  
DS2505 [CX0001]  
DS2506 [CX0001]  
DS4510@uSOP10 [CX1016]  
DS4550@TSSOP20 [CX1000]  
MAX9669@QFN28 [CX4013]  
MAX9674@QFN28(LD) [CX4013]

DS1685-3 [CX0001]  
DS1685-5 [CX0001]  
DS1687-3 [CX0001]  
DS17287-3 [CX0001]  
DS1742 [CX0001]  
DS1743 [CX0001]  
DS1743W [CX0001]  
DS1744 [CX0001]  
DS1744W [CX0001]  
DS1746 [CX0001]  
DS1747 [CX0001]  
DS1747PS [CX2068]  
DS1747WP [CX2068]  
DS17487-3 [CX0001]  
DS17887-3 [CX0001]  
DS2430A@TO-92 [CX0001]  
DS2431@TO-92 [CX0001]  
DS2432P@TSOC6 [CX1066]  
DS2433S(3.9)@SOIC8 [CX1045]  
DS2502 [CX0001]  
DS2502S@SOIC8 [CX1045]  
DS2502UNW@SOIC8 [CX1045]  
DS2502UNW@TSOC6 [CX1066]  
DS2505S@TSOC6 [CX1066]  
DS2506S@SOIC8 [CX1045]  
DS4520@TSSOP16 [CX1000]  
MAX9668@QFN20 [CX4025]  
MAX9674@QFN28 [CX4013]

## MICROCONTROLLER

71M6513H-IGT [CX3021-7]  
71M6513-IGT [CX3021-7]  
71M6521BE-IGT [CX3011-13]  
71M6521DE-IGT [CX3011-13]  
71M6521FE-IGT [CX3011-13]  
BQ2022ADBZR [CX1041]  
BQ2022DBZR [CX1041]  
DS5000 [ 8K] [CX0001]  
DS5000T [ 8K] [CX0001]  
DS87C520 [CX0001]  
DS87C520@TQFP44 [CX3003]  
DS89C420(rev.A)@PLCC44 [CX2044]  
MAX6889@QFN32 [CX4015]  
MAX9696@QFN24(left down) [CX4012]

71M6513H-IGTR [CX3021-7]  
71M6513-IGTR [CX3021-7]  
71M6521BE-IM [CX4026-1]  
71M6521DE-IM [CX4026-1]  
71M6521FE-IM [CX4026-1]  
BQ2022ALPR [CX0001]  
BQ2022LPR [CX0001]  
DS5000 [32K] [CX0001]  
DS5000T [32K] [CX0001]  
DS87C520@PLCC44 [CX2044]  
DS89C420(rev.A) [CX0001]  
DS89C420(rev.A)@TQFP44 [CX3003]  
MAX9696@QFN24 [CX4012]

## MAXWELL

### E (E) PROM/FRAM/NVRAM

28C010 [CX0001]  
28C010@TSOP32 [CX1002]  
28C010T@PLCC32 [CX2032]  
28C011 [CX0001]  
28C011@TSOP32 [CX1002]  
28C011T@PLCC32 [CX2032]

28C010@PLCC32 [CX2032]  
28C010T [CX0001]  
28C010T@TSOP32 [CX1002]  
28C011@PLCC32 [CX2032]  
28C011T [CX0001]  
28C011T@TSOP32 [CX1002]

# MEGAWIN

## E (E) PROM/FRAM/NVRAM

MM25SB512@SOIC8 [CX1045]  
MM29F040@PLCC32 [CX2032]  
MM29LF040 [CX0001]  
MM29LF040@TSOP32 [CX1002]  
MM29F040 [CX0001]  
MM29F040@TSOP32 [CX1002]  
MM29LF040@PLCC32 [CX2032]

## MICROCONTROLLER

MG87FE51AE [CX0001]  
MG87FE51AP@PLCC44 [CX2044]  
MG87FE52AF@TQFP44 [CX3002]  
MG87FL51AE [CX0001]  
MG87FL51AP@PLCC44 [CX2044]  
MG87FL52AF@TQFP44 [CX3002]  
MPC82E52AE [CX0001]  
MPC82E52AT@SSOP20 [CX1001]  
MPC82E54AE2 [CX0001]  
MPC82E54AS@SOP20 [CX1033]  
MPC82E54AT@SSOP20 [CX1001]  
MPC82G516AD@LQFP48 [CX3007]  
MPC82G516AF@PQFP44 [CX3002]  
MPC82L52AE [CX0001]  
MPC82L52AT@SSOP20 [CX1001]  
MPC82L54AE2 [CX0001]  
MPC82L54AS@SOP20 [CX1033]  
MPC82L54AT@SSOP20 [CX1001]  
MPC89E515AE [CX0001]  
MPC89E515AP@PLCC44 [CX2044]  
MPC89E51AF@PQFP44 [CX3002]  
MPC89E52AE [CX0001]  
MPC89E52AP@PLCC44 [CX2044]  
MPC89E53AF@PQFP44 [CX3002]  
MPC89E54AE [CX0001]  
MPC89E54AP@PLCC44 [CX2044]  
MPC89E58AF@PQFP44 [CX3002]  
MPC89L515AE [CX0001]  
MPC89L515AP@PLCC44 [CX2044]  
MPC89L516X2@PLCC44 [CX2044]  
MPC89L51AE [CX0001]  
MPC89L51AP@PLCC44 [CX2044]  
MPC89L52AF@PQFP44 [CX3002]  
MPC89L53AE [CX0001]  
MPC89L53AP@PLCC44 [CX2044]  
MPC89L54AF@PQFP44 [CX3002]  
MPC89L556X2 [CX0001]  
MPC89L556X2@TQFP44 [CX3003]  
MPC89L58AF@PQFP44 [CX3002]  
MG87FE51AF@TQFP44 [CX3002]  
MG87FE52AE [CX0001]  
MG87FE52AP@PLCC44 [CX2044]  
MG87FL51AF@TQFP44 [CX3002]  
MG87FL52AE [CX0001]  
MG87FL52AP@PLCC44 [CX2044]  
MPC82E52AS@SOP20 [CX1033]  
MPC82E54AE [CX0001]  
MPC82E54AP@PLCC32 [CX2032]  
MPC82E54AS2@SOP28 [CX1033]  
MPC82E54AT2@SSOP28 [CX1001]  
MPC82G516AE [CX0001]  
MPC82G516AP@PLCC44 [CX2044]  
MPC82L52AS@SOP20 [CX1033]  
MPC82L54AE [CX0001]  
MPC82L54AP@PLCC32 [CX2032]  
MPC82L54AS2@SOP28 [CX1033]  
MPC82L54AT2@SSOP28 [CX1001]  
MPC89E515AF@PQFP44 [CX3002]  
MPC89E51AE [CX0001]  
MPC89E51AP@PLCC44 [CX2044]  
MPC89E52AF@PQFP44 [CX3002]  
MPC89E53AE [CX0001]  
MPC89E53AP@PLCC44 [CX2044]  
MPC89E54AF@PQFP44 [CX3002]  
MPC89E58AE [CX0001]  
MPC89E58AP@PLCC44 [CX2044]  
MPC89L515AF@PQFP44 [CX3002]  
MPC89L516X2 [CX0001]  
MPC89L516X2@TQFP44 [CX3003]  
MPC89L51AF@PQFP44 [CX3002]  
MPC89L52AE [CX0001]  
MPC89L52AP@PLCC44 [CX2044]  
MPC89L53AF@PQFP44 [CX3002]  
MPC89L54AE [CX0001]  
MPC89L54AP@PLCC44 [CX2044]  
MPC89L556X2@PLCC44 [CX2044]  
MPC89L58AE [CX0001]  
MPC89L58AP@PLCC44 [CX2044]

# MEMOCOM

## E (E) PROM/FRAM/NVRAM

KI01602AB(Ga1)@FBGA66 [CX5005]	KI01602AB(Gb1)@FBGA66 [CX5026]
KI01602AT(Ga1)@FBGA66 [CX5005]	KI01602AT(Gb1)@FBGA66 [CX5026]
KI01604AB(Ga1)@FBGA58 [CX5005]	KI01604AB(Gb1)@FBGA66 [CX5005]
KI01604AT(Ga1)@FBGA58 [CX5005]	KI01604AT(Gb1)@FBGA66 [CX5005]
KI01608AB(Ga1)@FBGA58 [CX5005]	KI01608AB(Gb1)@FBGA66 [CX5005]
KI01608AT(Ga1)@FBGA58 [CX5005]	KI01608AT(Gb1)@FBGA66 [CX5005]
KI03204AB(Ga1)@FBGA58 [CX5005]	KI03204AB(Gb1)@FBGA66 [CX5005]
KI03204AT(Ga1)@FBGA58 [CX5005]	KI03204AT(Gb1)@FBGA66 [CX5005]
KI03204BB@FBGA58 [CX5005]	KI03204BT@FBGA58 [CX5005]
KI03208AB(Ga1)@FBGA58 [CX5005]	KI03208AB(Gb1)@FBGA66 [CX5005]
KI03208AT(Ga1)@FBGA58 [CX5005]	KI03208AT(Gb1)@FBGA66 [CX5005]
KI03208BB@FBGA58 [CX5005]	KI03208BT@FBGA58 [CX5005]
KI03216AB(Ha1)@FBGA88 [CX5005]	KI03216AT(Ha1)@FBGA88 [CX5005]
KI06416AB(Ha1)@FBGA88 [CX5005]	KI06416AT(Ha1)@FBGA88 [CX5005]
KIB2832AU(Ha1)@FBGA88 [CX5005]	KIB2864AU(Ha1)@FBGA88 [CX5005]
KIB6432AT(Ha1)@FBGA88 [CX5005]	KIP2832AU(Ha1)@FBGA88 [CX5005]
KIP2864AU(Ha1)@FBGA88 [CX5005]	KIP6432AB(Ha1)@FBGA88 [CX5005]
KIP6432AT(Ha1)@FBGA88 [CX5005]	KIX2832DU(HY1)@FBGA56 [CX5094]
KIX2864EU(HY1)@FBGA56 [CX5094]	KIX6432AT(HY1)@FBGA56 [CX5094]
KS01602AB(Gh)@FBGA56 [CX5045]	KS01602AT(Gh)@FBGA56 [CX5045]
KS01604AB(Gh)@FBGA56 [CX5045]	KS01604AT(Gh)@FBGA56 [CX5045]
KS03204AB(Gh)@FBGA56 [CX5045]	KS03204AT(Gh)@FBGA56 [CX5045]
KS03204CB@FBGA56 [CX5045]	KS03204CT@FBGA56 [CX5045]
KS03208AB(Gh)@FBGA56 [CX5045]	KS03208AT(Gh)@FBGA56 [CX5045]
KS03208BB@FBGA56 [CX5045]	KS03208BT@FBGA56 [CX5045]
KS03208BT@FBGA56(XW) [CX5005]	KS03216AB(Hh1)@FBGA56 [CX5045]
KS03216AT(Hh1)@FBGA56 [CX5045]	KS06416AB(Hh1)@FBGA56 [CX5045]
KS06416AT(Hh1)@FBGA56 [CX5045]	KSP2832AU(Hs1)@FBGA64 [CX5001]
KSP2832EU(HT1)@FBGA84 [CX5001]	KSP2864AU(Hs1)@FBGA64 [CX5001]
KSP3216BB@FBGA56 [CX5045]	KSP3216BT@FBGA56 [CX5045]
KSP6416BB@FBGA56 [CX5045]	KSP6416BT@FBGA56 [CX5045]
KSP6432AB@FBGA56 [CX5045]	KSP6432AT@FBGA56 [CX5045]
KSP6432AT@FBGA56(XW) [CX5005]	KTF29028AU@TSOP56 [CX1011]

## MICON

### MICROCONTROLLER

MDT10P21(dip18) [CX0001]	MDT10P21(dip20) [CX0001]
MDT10P21(dip22) [CX0001]	MDT10P21@SOP18 [CX1033]
MDT10P21@SOP20 [CX1033]	MDT10P21@SOP24 [CX1033]
MDT10P22(dip18) [CX0001]	MDT10P22(dip20) [CX0001]
MDT10P22(dip22) [CX0001]	MDT10P22@SOP18 [CX1033]
MDT10P22@SOP20 [CX1033]	MDT10P22@SOP24 [CX1033]
MDT10P23(dip18) [CX0001]	MDT10P23(dip20) [CX0001]
MDT10P23(dip22) [CX0001]	MDT10P23@SOP18 [CX1033]
MDT10P23@SOP20 [CX1033]	MDT10P23@SOP24 [CX1033]
MDT10P41A1 [CX0001]	MDT10P41A1@SOP16 [CX1033]
MDT10P41A2 [CX0001]	MDT10P41A2@SOP16 [CX1033]
MDT10P43P11 [CX0001]	MDT10P43P21 [CX0001]
MDT10P43S11@SOP18 [CX1033]	MDT10P43S21@SOP20 [CX1033]
MDT10P55A1 [CX0001]	MDT10P55A1@SOP14 [CX1030]
MDT10P55A2 [CX0001]	MDT10P55A2@SOP14 [CX1030]
MDT10P55A3 [CX0001]	MDT10P55A3@SOP14 [CX1030]
MDT10P55A4 [CX0001]	MDT10P55A4@SOP14 [CX1030]
MDT10P55B1 [CX0001]	MDT10P55B1@SOP14 [CX1030]
MDT10P55B2 [CX0001]	MDT10P55B2@SOP14 [CX1030]
MDT10P55B3 [CX0001]	MDT10P55B3@SOP14 [CX1030]

MDT10P55B4 [CX0001]	MDT10P55B4@SOP14 [CX1030]
MDT10P61 [CX0001]	MDT10P61@SOP18 [CX1033]
MDT10P61@SSOP20 [CX1026]	MDT10P62 [CX0001]
MDT10P62@SOP28 [CX1033]	MDT10P62@SSOP28 [CX1026]
MDT10P621 [CX0001]	MDT10P621@SOP28 [CX1033]
MDT10P621@SSOP28 [CX1026]	MDT10P64 [CX0001]
MDT10P64@PLCC44 [CX2044]	MDT10P64@QFP44 [CX3046]
MDT10P65(dip28) [CX0001]	MDT10P65(dip42) [CX0001]
MDT10P65@SDIP42 [CX0042]	MDT10P65@SOP28 [CX1033]
MDT10P651 [CX0001]	MDT10P651@PLCC44 [CX2044]
MDT10P651@QFP44 [CX3046]	MDT10P65A1@QFP44 [CX3046]
MDT10P65A2@QFP44 [CX3046]	MDT10P72 [CX0001]
MDT10P72@SOP28 [CX1033]	MDT10P72@SSOP28 [CX1026]
MDT10P721 [CX0001]	MDT10P721@SOP28 [CX1033]
MDT10P721@SSOP28 [CX1026]	MDT10P73 [CX0001]
MDT10P73@SOP28 [CX1033]	MDT10P73@SSOP28 [CX1026]
MDT10P74 [CX0001]	MDT10P74@PLCC44 [CX2044]
MDT10P74@QFP44 [CX3046]	MDT2005 [CX0001]
MDT2005@SOP18 [CX1033]	MDT2005@SSOP20 [CX1026]
MDT2010 [CX0001]	MDT2010@SOP18 [CX1033]
MDT2010@SSOP20 [CX1026]	MDT2020 [CX0001]
MDT2020@SOP28 [CX1033]	MDT2020@SSOP28 [CX1026]
MDT2030 [CX0001]	MDT2030@SOP18 [CX1033]
MDT2030@SSOP20 [CX1026]	MDT2050 [CX0001]
MDT2050@SOP18 [CX1033]	MDT2050@SSOP20 [CX1026]
MDT2051 [CX0001]	MDT2051@SOP18 [CX1033]
MDT2051@SSOP20 [CX1026]	MDT2060 [CX0001]
MDT2060@SOP18 [CX1033]	MDT2060@SSOP20 [CX1026]

## MICROCHIP

### E (E) PROM/FRAM/NVRAM

23A256 [CX0001]	23A256@SOIC8 [CX1045]
23A256@TSSOP8 [CX1059]	23A640 [CX0001]
23A640@SOIC8 [CX1045]	23A640@TSSOP8 [CX1059]
23K256 [CX0001]	23K256@SOIC8 [CX1045]
23K256@TSSOP8 [CX1059]	23K640 [CX0001]
23K640@SOIC8 [CX1045]	23K640@TSSOP8 [CX1059]
24AA00 [CX0001]	24AA00@DFN8 [CX4002]
24AA00@SOIC8 [CX1045]	24AA00@SOT-23 [CX1041]
24AA00@TSSOP8 [CX1059]	24AA01 [CX0001]
24AA01@DFN8 [CX4002]	24AA01@SOIC8 [CX1045]
24AA01@TSSOP8 [CX1059]	24AA014 [CX0001]
24AA014@SOIC8 [CX1045]	24AA014@TSSOP8 [CX1059]
24AA02 [CX0001]	24AA02@DFN8 [CX4002]
24AA02@MSOP8 [CX1015]	24AA02@SOIC8 [CX1045]
24AA02@SOT-23-5 [CX1041]	24AA02@TSSOP8 [CX1059]
24AA024 [CX0001]	24AA024@DFN8 [CX4002]
24AA024@MSOP8 [CX1015]	24AA024@SOIC8 [CX1045]
24AA024@TSSOP8 [CX1059]	24AA025 [CX0001]
24AA025@DFN8 [CX4002]	24AA025@MSOP8 [CX1015]
24AA025@SOIC8 [CX1045]	24AA025@TSSOP8 [CX1059]
24AA04 [CX0001]	24AA04@DFN8 [CX4002]
24AA04@SOIC8 [CX1045]	24AA04@TSSOP8 [CX1059]
24AA08 [CX0001]	24AA08@DFN8 [CX4002]
24AA08@SOIC8 [CX1045]	24AA08@TSSOP8 [CX1059]
24AA1025 [CX0001]	24AA1025@SOIC8 [CX1044]



24AA1025@TSSOP8 [CX1059] 24AA1026 [CX0001]  
24AA1026@SOIC8 [CX1044] 24AA1026@TSSOP8 [CX1044]  
24AA128 [CX0001] 24AA128@DFN8 [CX4002]  
24AA128@MSOP8 [CX1015] 24AA128@SOIC8 [CX1045]  
24AA128@TSSOP14 [CX1000] 24AA128@TSSOP8 [CX1059]  
24AA16 [CX0001] 24AA16@DFN8 [CX4002]  
24AA16@SOIC8 [CX1045] 24AA16@TSSOP8 [CX1059]  
24AA164 [CX0001] 24AA164@SOIC8 [CX1045]  
24AA164@TSSOP8 [CX1059] 24AA174 [CX0001]  
24AA174@SOIC8 [CX1045] 24AA174@TSSOP8 [CX1059]  
24AA256 [CX0001] 24AA256@DFN8 [CX4002]  
24AA256@MSOP8 [CX1015] 24AA256@SOIC8 [CX1045]  
24AA256@TSSOP14 [CX1000] 24AA256@TSSOP8 [CX1059]  
24AA32 [CX0001] 24AA32(Rotated)@TSSOP8 [CX1059]  
24AA32@DFN8 [CX4002] 24AA32@MSOP8 [CX1015]  
24AA32@SOIC8 [CX1045] 24AA32@TSSOP8 [CX1059]  
24AA32A [CX0001] 24AA32A(Rotated)@TSSOP8 [CX1059]  
24AA32A@DFN8 [CX4002] 24AA32A@MSOP8 [CX1015]  
24AA32A@SOIC8 [CX1045] 24AA32A@SOT-23 [CX1041]  
24AA32A@TSSOP8 [CX1059] 24AA32AF [CX0001]  
24AA32AF(Rotated)@TSSOP8 [CX1059] 24AA32AF@MSOP8 [CX1015]  
24AA32AF@DFN8 [CX4002] 24AA32AF@TSSOP8 [CX1059]  
24AA32AF@SOIC8 [CX1045] 24AA512@DFN8 [CX4005]  
24AA512 [CX0001] 24AA512@TSSOP14 [CX1030]  
24AA512@SOIC8 [CX1044] 24AA515@SOIC8 [CX1044]  
24AA515 [CX0001] 24AA52@DFN8 [CX4002]  
24AA52 [CX0001] 24AA52@SOIC8 [CX1045]  
24AA52@MSOP8 [CX1015] 24AA64 [CX0001]  
24AA52@TSSOP8 [CX1059] 24AA64@DFN8 [CX4002]  
24AA64(Rotated)@TSSOP8 [CX1059] 24AA64@SOIC8 [CX1045]  
24AA64@MSOP8 [CX1015] 24AA64F [CX0001]  
24AA64@TSSOP8 [CX1059] 24AA64F@DFN8 [CX4002]  
24AA64F(Rotated)@TSSOP8 [CX1059] 24AA64F@SOIC8 [CX1045]  
24AA64F@MSOP8 [CX1015] 24AA65 [CX0001]  
24AA64F@TSSOP8 [CX1059] 24AA65@SOIC8 [CX1045]  
24AA65@DFN8 [CX4002] 24C00 [CX0001]  
24AA65@TSSOP8 [CX1059] 24C00@SOIC8 [CX1045]  
24C00@DFN8 [CX4002] 24C00@TSSOP8 [CX1059]  
24C00@SOT-23 [CX1041] 24C01A [CX0001]  
24C01 [CX0001] 24C01C [CX0001]  
24C01A@SOIC8 [CX1045] 24C01C@TSSOP8 [CX1059]  
24C01C@SOIC8 [CX1045] 24C02A [CX0001]  
24C02 [CX0001] 24C02C [CX0001]  
24C02A@SOIC8 [CX1045] 24C02C@TSSOP8 [CX1059]  
24C02C@SOIC8 [CX1045] 24C04A [CX0001]  
24C04 [CX0001] 24C04A@TSSOP8 [CX1059]  
24C04A@SOIC8 [CX1045] 24C08@SOIC8 [CX1045]  
24C08 [CX0001] 24C08B@SOIC8 [CX1045]  
24C08B [CX0001] 24C16@SOIC8 [CX1045]  
24C16 [CX0001] 24C16B@SOIC8 [CX1045]  
24C16B [CX0001] 24C32@DFN8 [CX4002]  
24C32 [CX0001] 24C64 [CX0001]  
24C32@SOIC8 [CX1045] 24C64@SOIC8 [CX1045]  
24C64@DFN8 [CX4002] 24C65 [CX0001]  
24C64@TSSOP8 [CX1059] 24C65@SOIC8 [CX1045]  
24C65@DFN8 [CX4002] 24FC1025@SOIC8 [CX1044]  
24FC1025 [CX0001] 24FC1026 [CX0001]  
24FC1025@TSSOP8 [CX1059] 24FC1026@TSSOP8 [CX1044]  
24FC1026@SOIC8 [CX1044]

24FC128 [CX0001] 24FC128@DFN8 [CX4002]  
24FC128@MSOP8 [CX1015] 24FC128@SOIC8 [CX1045]  
24FC128@TSSOP14 [CX1000] 24FC128@TSSOP8 [CX1059]  
24FC256 [CX0001] 24FC256@DFN8 [CX4002]  
24FC256@MSOP8 [CX1015] 24FC256@SOIC8 [CX1045]  
24FC256@TSSOP14 [CX1000] 24FC256@TSSOP8 [CX1059]  
24FC32 [CX0001] 24FC32@DFN8 [CX4002]  
24FC32@SOIC8 [CX1045] 24FC512 [CX0001]  
24FC512@DFN8 [CX4005] 24FC512@SOIC8 [CX1044]  
24FC512@TSSOP14 [CX1030] 24FC515 [CX0001]  
24FC515@SOIC8 [CX1044] 24FC64 [CX0001]  
24FC64(Rotated)@TSSOP8 [CX1059] 24FC64@DFN8 [CX4002]  
24FC64@MSOP8 [CX1015] 24FC64@SOIC8 [CX1045]  
24FC64@TSSOP8 [CX1059] 24FC65 [CX0001]  
24FC65@DFN8 [CX4002] 24FC65@SOIC8 [CX1045]  
24LC00 [CX0001] 24LC00@DFN8 [CX4002]  
24LC00@SOIC8 [CX1045] 24LC00@SOT-23 [CX1041]  
24LC00@TSSOP8 [CX1059] 24LC01 [CX0001]  
24LC014 [CX0001] 24LC014@SOIC8 [CX1045]  
24LC014@TSSOP8 [CX1059] 24LC01B [CX0001]  
24LC01B@DFN8 [CX4002] 24LC01B@SOIC8 [CX1045]  
24LC01B@TSSOP8 [CX1059] 24LC02 [CX0001]  
24LC024 [CX0001] 24LC024@SOIC8 [CX1045]  
24LC024@TSSOP8 [CX1059] 24LC025 [CX0001]  
24LC025@SOIC8 [CX1045] 24LC025@TSSOP8 [CX1059]  
24LC02B [CX0001] 24LC02B@DFN8 [CX4002]  
24LC02B@MSOP8 [CX1015] 24LC02B@SOIC8 [CX1045]  
24LC02B@SOT-23-5 [CX1041] 24LC02B@TSSOP8 [CX1059]  
24LC04 [CX0001] 24LC04B [CX0001]  
24LC04B@DFN8 [CX4002] 24LC04B@SOIC8 [CX1045]  
24LC04B@TSSOP8 [CX1059] 24LC08 [CX0001]  
24LC08B [CX0001] 24LC08B@DFN8 [CX4002]  
24LC08B@SOIC8 [CX1045] 24LC08B@TSSOP8 [CX1059]  
24LC1025 [CX0001] 24LC1025@SOIC8 [CX1044]  
24LC1025@TSSOP8 [CX1059] 24LC1026 [CX0001]  
24LC1026@SOIC8 [CX1044] 24LC1026@TSSOP8 [CX1044]  
24LC128 [CX0001] 24LC128@DFN8 [CX4002]  
24LC128@MSOP8 [CX1015] 24LC128@SOIC8 [CX1045]  
24LC128@TSSOP14 [CX1000] 24LC128@TSSOP8 [CX1059]  
24LC16 [CX0001] 24LC16@MSOP8 [CX1015]  
24LC16@SOIC8 [CX1045] 24LC164 [CX0001]  
24LC164@SOIC8 [CX1045] 24LC16B [CX0001]  
24LC16B@DFN8 [CX4002] 24LC16B@SOIC8 [CX1045]  
24LC16B@TSSOP8 [CX1059] 24LC174 [CX0001]  
24LC174@SOIC8 [CX1045] 24LC21 [CX0001]  
24LC21@SOIC8 [CX1045] 24LC21A [CX0001]  
24LC21A@SOIC8 [CX1045] 24LC22A [CX0001]  
24LC22A@SOIC8 [CX1045] 24LC256 [CX0001]  
24LC256@DFN8 [CX4002] 24LC256@MSOP8 [CX1015]  
24LC256@SOIC8(150mil) [CX1045] 24LC256@SOIC8(200mil) [CX1044]  
24LC256@TSSOP14 [CX1000] 24LC256@TSSOP8 [CX1059]  
24LC32 [CX0001] 24LC32@SOIC8 [CX1045]  
24LC32A [CX0001] 24LC32A@DFN8 [CX4002]  
24LC32A@SOIC8 [CX1045] 24LC32A@SOT-23 [CX1041]  
24LC32A@TSSOP8 [CX1059] 24LC32AF [CX0001]  
24LC32AF@DFN8 [CX4002] 24LC32AF@SOIC8 [CX1045]  
24LC32AF@TSSOP8 [CX1059] 24LC512 [CX0001]  
24LC512@DFN8 [CX4005] 24LC512@SOIC8 [CX1044]  
24LC512@TSSOP14 [CX1030] 24LC515 [CX0001]

24LC515@SOIC8 [CX1044] 24LC64 [CX0001]  
24LC64(Rotated)@TSSOP8 [CX1059] 24LC64(SM)@SOIC8 [CX1044]  
24LC64@DFN8 [CX4002] 24LC64@MSOP8 [CX1015]  
24LC64@SOIC8 [CX1045] 24LC64@TSSOP8 [CX1059]  
24LC64F [CX0001] 24LC64F(Rotated)@TSSOP8 [CX1059]  
24LC64F@DFN8 [CX4002] 24LC64F@MSOP8 [CX1015]  
24LC64F@SOIC8 [CX1045] 24LC64F@TSSOP8 [CX1059]  
24LC65 [CX0001] 24LC65@DFN8 [CX4002]  
24LC65@SOIC8 [CX1045] 24LCS21 [CX0001]  
24LCS21@SOIC8 [CX1045] 24LCS21A [CX0001]  
24LCS21A@SOIC8 [CX1045] 24LCS22 [CX0001]  
24LCS22@SOIC8 [CX1045] 24LCS22A [CX0001]  
24LCS22A@SOIC8 [CX1045] 24LCS52 [CX0001]  
24LCS52@DFN8 [CX4002] 24LCS52@MSOP8 [CX1015]  
24LCS52@SOIC8 [CX1045] 24LCS52@TSSOP8 [CX1059]  
24LCS61 [CX0001] 24LCS61@SOIC8 [CX1045]  
24LCS62 [CX0001] 24LCS62@SOIC8 [CX1045]  
24VL014 [CX0001] 24VL014@MSOP8 [CX1015]  
24VL014@SOIC8 [CX1045] 24VL014@SOT-23 [CX1041]  
24VL014@TDFN8 [CX4002] 24VL014@TSSOP8 [CX1059]  
24VL024 [CX0001] 24VL024@MSOP8 [CX1015]  
24VL024@SOIC8 [CX1045] 24VL024@TDFN8 [CX4002]  
24VL024@TSSOP8 [CX1059] 24VL025 [CX0001]  
24VL025@MSOP8 [CX1015] 24VL025@SOIC8 [CX1045]  
24VL025@SOT-23 [CX1041] 24VL025@TDFN8 [CX4002]  
24VL025@TSSOP8 [CX1059] 25A512@SOIC8 [CX1045]  
25A512@TSSOP8 [CX1059] 25AA010A [CX0001]  
25AA010A@DFN8 [CX4005] 25AA010A@MSOP8 [CX1044]  
25AA010A@SOIC8 [CX1045] 25AA010A@SOT-23 [CX1041]  
25AA010A@TSSOP8 [CX1059]  
25AA010A[X-Rotated]@TSSOP8 [CX1059]  
25AA020A [CX0001] 25AA020A@DFN8 [CX4005]  
25AA020A@MSOP8 [CX1044] 25AA020A@SOIC8 [CX1045]  
25AA020A@SOT-23 [CX1041] 25AA020A@TSSOP8 [CX1059]  
25AA020A[X-Rotated]@TSSOP8 [CX1059]  
25AA040 [CX0001] 25AA040@SOIC8 [CX1045]  
25AA040@TSSOP8 [CX1059] 25AA040A [CX0001]  
25AA040A@DFN8 [CX4005] 25AA040A@MSOP8 [CX1044]  
25AA040A@SOIC8 [CX1045] 25AA040A@SOT-23 [CX1041]  
25AA040A@TSSOP8 [CX1059]  
25AA040A[X-Rotated]@TSSOP8 [CX1059]  
25AA080 [CX0001] 25AA080@SOIC8 [CX1045]  
25AA080A [CX0001] 25AA080A@MSOP8 [CX1044]  
25AA080A@SOIC8 [CX1045] 25AA080A@TSSOP8 [CX1059]  
25AA080B [CX0001] 25AA080B@MSOP8 [CX1044]  
25AA080B@SOIC8 [CX1045] 25AA080B@TSSOP8 [CX1059]  
25AA080C [CX0001] 25AA080C@MSOP8 [CX1044]  
25AA080C@SOIC8 [CX1045] 25AA080C@TSSOP8 [CX1059]  
25AA080D [CX0001] 25AA080D@MSOP8 [CX1044]  
25AA080D@SOIC8 [CX1045] 25AA080D@TSSOP8 [CX1059]  
25AA1024 [CX0001] 25AA1024@DFN8 [CX4005]  
25AA1024@SOIC8 [CX1045] 25AA1024@SOI J8 [CX1044]  
25AA128 [CX0001] 25AA128@DFN8 [CX4005]  
25AA128@SOIC8(4.0) [CX1045] 25AA128@SOIC8(5.4) [CX1044]  
25AA128@TSSOP8 [CX1059]  
25AA128[X-Rotated]@TSSOP8 [CX1059]  
25AA160 [CX0001] 25AA160@SOIC8 [CX1045]  
25AA160A [CX0001] 25AA160A@MSOP8 [CX1044]  
25AA160A@SOIC8 [CX1045] 25AA160A@TSSOP8 [CX1059]

25AA160B [CX0001] 25AA160B@MSOP8 [CX1044]  
25AA160B@SOIC8 [CX1045] 25AA160B@TSSOP8 [CX1059]  
25AA160C [CX0001] 25AA160C@MSOP8 [CX1044]  
25AA160C@SOIC8 [CX1045] 25AA160C@TDFN8 [CX4002]  
25AA160C@TSSOP8 [CX1059] 25AA160D [CX0001]  
25AA160D@MSOP8 [CX1044] 25AA160D@SOIC8 [CX1045]  
25AA160D@TDFN8 [CX4002] 25AA160D@TSSOP8 [CX1059]  
25AA256 [CX0001] 25AA256@DFN8 [CX4005]  
25AA256@SOIC8(4.0) [CX1045] 25AA256@SOIC8(5.4) [CX1044]  
25AA256@TSSOP8 [CX1059]  
25AA256[X-Rotated]@TSSOP8 [CX1059]  
25AA320 [CX0001] 25AA320@SOIC8 [CX1045]  
25AA320@TSSOP14 [CX1000] 25AA320@TSSOP8 [CX1059]  
25AA320A [CX0001] 25AA320A@DFN8 [CX4005]  
25AA320A@MSOP8 [CX1044] 25AA320A@SOIC8 [CX1045]  
25AA320A@TDFN8 [CX4002] 25AA320A@TSSOP8 [CX1059]  
25AA320A@XTSSOP8 [CX1059] 25AA512 [CX0001]  
25AA512@DFN8 [CX4005] 25AA512@SOIC8 [CX1045]  
25AA512@SOIJ8 [CX1044] 25AA640 [CX0001]  
25AA640@SOIC8 [CX1045] 25AA640@TSSOP8 [CX1059]  
25AA640A [CX0001] 25AA640A@DFN8 [CX4005]  
25AA640A@MSOP8 [CX1044] 25AA640A@SOIC8 [CX1045]  
25AA640A@TDFN8 [CX4002] 25AA640A@TSSOP8 [CX1059]  
25AA640A@XTSSOP8 [CX1059] 25C040 [CX0001]  
25C040@SOIC8 [CX1045] 25C040@TSSOP8 [CX1059]  
25C080 [CX0001] 25C080@SOIC8 [CX1045]  
25C160 [CX0001] 25C160@SOIC8 [CX1045]  
25C320 [CX0001] 25C320@SOIC8 [CX1045]  
25C320@TSSOP14 [CX1000] 25C320@TSSOP8 [CX1059]  
25C640 [CX0001] 25C640@SOIC8 [CX1045]  
25C640@TSSOP8 [CX1059] 25LC010A [CX0001]  
25LC010A@DFN8 [CX4005] 25LC010A@MSOP8 [CX1044]  
25LC010A@SOIC8 [CX1045] 25LC010A@SOT-23 [CX1041]  
25LC010A@TSSOP8 [CX1059]  
25LC010A[X-Rotated]@TSSOP8 [CX1059]  
25LC020A [CX0001] 25LC020A@DFN8 [CX4005]  
25LC020A@MSOP8 [CX1044] 25LC020A@SOIC8 [CX1045]  
25LC020A@SOT-23 [CX1041] 25LC020A@TSSOP8 [CX1059]  
25LC020A[X-Rotated]@TSSOP8 [CX1059]  
25LC040 [CX0001] 25LC040@SOIC8 [CX1045]  
25LC040@TSSOP8 25LC040A [CX0001]  
25LC040A@DFN8 [CX4005] 25LC040A@MSOP8 [CX1044]  
25LC040A@SOIC8 [CX1045] 25LC040A@SOT-23 [CX1041]  
25LC040A@TSSOP8 [CX1059]  
25LC040A[X-Rotated]@TSSOP8 [CX1059]  
25LC080 [CX0001] 25LC080@SOIC8 [CX1045]  
25LC080A [CX0001] 25LC080A@MSOP8 [CX1044]  
25LC080A@SOIC8 [CX1045] 25LC080A@TSSOP8 [CX1059]  
25LC080B [CX0001] 25LC080B@MSOP8 [CX1044]  
25LC080B@SOIC8 [CX1045] 25LC080B@TSSOP8 [CX1059]  
25LC080C [CX0001] 25LC080C@MSOP8 [CX1044]  
25LC080C@SOIC8 [CX1045] 25LC080C@TSSOP8 [CX1059]  
25LC080D [CX0001] 25LC080D@MSOP8 [CX1044]  
25LC080D@SOIC8 [CX1045] 25LC080D@TSSOP8 [CX1059]  
25LC1024 [CX0001] 25LC1024@DFN8 [CX4005]  
25LC1024@SOIC8 [CX1045] 25LC1024@SOIJ8 [CX1044]  
25LC128 [CX0001] 25LC128@DFN8 [CX4005]  
25LC128@SOIC8(4.0) [CX1045] 25LC128@SOIC8(5.4) [CX1044]  
25LC128@TSSOP8 [CX1059]

25LC128[X-Rotated]@TSSOP8 [CX1059]  
25LC160 [CX0001]  
25LC160A [CX0001]  
25LC160A@SOIC8 [CX1045]  
25LC160B [CX0001]  
25LC160B@SOIC8 [CX1045]  
25LC160C [CX0001]  
25LC160C@SOIC8 [CX1045]  
25LC160C@TSSOP8 [CX1059]  
25LC160D@MSOP8 [CX1044]  
25LC160D@TDFN8 [CX4002]  
25LC256 [CX0001]  
25LC256@SOIC8(4.0) [CX1045]  
25LC256@TSSOP8 [CX1059]  
25LC256[X-Rotated]@TSSOP8 [CX1059]  
25LC320 [CX0001]  
25LC320@TSSOP14 [CX1000]  
25LC320A [CX0001]  
25LC320A@MSOP8 [CX1044]  
25LC320A@TDFN8 [CX4002]  
25LC320A@XTSSOP8 [CX1059]  
25LC512@DFN8 [CX4005]  
25LC512@SOIJ8 [CX1044]  
25LC640@SOIC8 [CX1045]  
25LC640A [CX0001]  
25LC640A@MSOP8 [CX1044]  
25LC640A@TDFN8 [CX4002]  
25LC640A@XTSSOP8 [CX1059]  
27256@PLCC32 [CX2032]  
27C128@PLCC32 [CX2032]  
27C128A@PLCC32 [CX2032]  
27C256@PLCC32 [CX2032]  
27C512 [CX0001]  
27C512A [CX0001]  
27C513 [CX0001]  
27C64@PLCC32 [CX2032]  
27HC1616 [CX0001]  
27HC1616L [CX0001]  
27HC191 [CX0001]  
27HC191@SOIC24 [CX1033]  
27HC256@PLCC32 [CX2032]  
27HC256L@PLCC32 [CX2032]  
27HC291@PLCC28 [CX2028]  
27HC416 [CX0001]  
27HC64 [CX0001]  
27HC64@SOIC28 [CX1033]  
27HC641@PLCC28 [CX2028]  
27HC641L [CX0001]  
27HC641L@SOIC24 [CX1033]  
27HC64L@PLCC32 [CX2032]  
27LV256 [CX0001]  
27LV64 [CX0001]  
2864 [CX0001]  
28C04 [CX0001]  
28C04@SOIC24 [CX1033]  
28C04A@PLCC32 [CX2032]  
28C04AF [CX0001]  
28C04AF@SOIC24 [CX1033]  
28C04F@PLCC32 [CX2032]  
25LC160@SOIC8 [CX1045]  
25LC160A@MSOP8 [CX1044]  
25LC160A@TSSOP8 [CX1059]  
25LC160B@MSOP8 [CX1044]  
25LC160B@TSSOP8 [CX1059]  
25LC160C@MSOP8 [CX1044]  
25LC160C@TDFN8 [CX4002]  
25LC160D [CX0001]  
25LC160D@SOIC8 [CX1045]  
25LC160D@TSSOP8 [CX1059]  
25LC256@DFN8 [CX4005]  
25LC256@SOIC8(5.4) [CX1044]  
25LC320(SN)@SOIC8 [CX1045]  
25LC320@TSSOP8 [CX1059]  
25LC320A@DFN8 [CX4005]  
25LC320A@SOIC8 [CX1045]  
25LC320A@TSSOP8 [CX1059]  
25LC512 [CX0001]  
25LC512@SOIC8 [CX1045]  
25LC640 [CX0001]  
25LC640@TSSOP8 [CX1059]  
25LC640A@DFN8 [CX4005]  
25LC640A@SOIC8 [CX1045]  
25LC640A@TSSOP8 [CX1059]  
27256 [CX0001]  
27C128 [CX0001]  
27C128A [CX0001]  
27C256 [CX0001]  
27C32A [CX0001]  
27C512@PLCC32 [CX2032]  
27C512A@PLCC32 [CX2032]  
27C64 [CX0001]  
27C64@SOIC28 [CX1033]  
27HC1616@PLCC44 [CX2044]  
27HC1616L@PLCC44 [CX2044]  
27HC191@PLCC28 [CX2028]  
27HC256 [CX0001]  
27HC256L [CX0001]  
27HC291 [CX0001]  
27HC291@SOIC24 [CX1033]  
27HC416@PLCC44 [CX2044]  
27HC64@PLCC32 [CX2032]  
27HC641 [CX0001]  
27HC641@SOIC24 [CX1033]  
27HC641L@PLCC28 [CX2028]  
27HC64L [CX0001]  
27HC64L@SOIC28 [CX1033]  
27LV256@PLCC32 [CX2032]  
2817 [CX0001]  
2864@PLCC32 [CX2032]  
28C04@PLCC32 [CX2032]  
28C04A [CX0001]  
28C04A@SOIC24 [CX1033]  
28C04AF@PLCC32 [CX2032]  
28C04F [CX0001]  
28C04F@SOIC24 [CX1033]

28C16 [CX0001] 28C16@PLCC32 [CX2032]  
28C16@SOIC24 [CX1033] 28C16A [CX0001]  
28C16A@PLCC32 [CX2032] 28C16A@SOIC24 [CX1033]  
28C16AF [CX0001] 28C16AF@PLCC32 [CX2032]  
28C16AF@SOIC24 [CX1033] 28C16F [CX0001]  
28C16F@PLCC32 [CX2032] 28C16F@SOIC24 [CX1033]  
28C17 [CX0001] 28C17@PLCC32 [CX2032]  
28C17@SOIC28 [CX1033] 28C17A [CX0001]  
28C17A@PLCC32 [CX2032] 28C17A@SOIC28 [CX1033]  
28C17AF [CX0001] 28C17AF@PLCC32 [CX2032]  
28C17AF@SOIC28 [CX1033] 28C17F [CX0001]  
28C17F@PLCC32 [CX2032] 28C17F@SOIC28 [CX1033]  
28C256 [CX0001] 28C256@PLCC32 [CX2032]  
28C256F [CX0001] 28C256F@PLCC32 [CX2032]  
28C64A [CX0001] 28C64A@PLCC32 [CX2032]  
28C64A@SOIC28 [CX1033] 28C64A@TSOP32 [CX1002]  
28C64AF [CX0001] 28C64AF@PLCC32 [CX2032]  
28C64AF@SOIC28 [CX1033] 28LV64A [CX0001]  
28LV64A@PLCC32 [CX2032] 28LV64A@SOIC28 [CX1033]  
28PC64 [CX0001] 28PC64@PLCC32 [CX2032]  
59C11 [CX0001] 59C11@SOIC8 [CX1045]  
85C72 [CX0001] 85C72@SOIC8 [CX1045]  
85C82 [CX0001] 85C82@SOIC8 [CX1045]  
85C92 [CX0001] 85C92@SOIC8 [CX1045]  
93AA46(08bit) [CX0001] 93AA46(08bit)@SOIC8 [CX1045]  
93AA46(16bit) [CX0001] 93AA46(16bit)@SOIC8 [CX1045]  
93AA46A(08bit) [CX0001] 93AA46A(08bit)@DFN8 [CX0001]  
93AA46A(08bit)@MSOP8 [CX1015] 93AA46A(08bit)@SOIC8 [CX1045]  
93AA46A(08bit)@SOT-23 [CX1041] 93AA46A(08bit)@TSSOP8 [CX1059]  
93AA46B(16bit) [CX0001] 93AA46B(16bit)@DFN8 [CX0001]  
93AA46B(16bit)@MSOP8 [CX1015] 93AA46B(16bit)@SOIC8 [CX1045]  
93AA46B(16bit)@SOT-23 [CX1041] 93AA46B(16bit)@TSSOP8 [CX1059]  
93AA46C(08bit) [CX0001] 93AA46C(08bit)@DFN8 [CX0001]  
93AA46C(08bit)@MSOP8 [CX1015] 93AA46C(08bit)@SOIC8 [CX1045]  
93AA46C(08bit)@TSSOP8 [CX1059] 93AA46C(16bit) [CX0001]  
93AA46C(16bit)@DFN8 [CX0001] 93AA46C(16bit)@MSOP8 [CX1015]  
93AA46C(16bit)@SOIC8 [CX1045] 93AA46C(16bit)@TSSOP8 [CX1059]  
93AA56(08bit) [CX0001] 93AA56(08bit)@SOIC8 [CX1045]  
93AA56(16bit) [CX0001] 93AA56(16bit)@SOIC8 [CX1045]  
93AA56A(08bit) [CX0001] 93AA56A(08bit)@DFN8 [CX0001]  
93AA56A(08bit)@MSOP8 [CX1015] 93AA56A(08bit)@SOIC8 [CX1045]  
93AA56A(08bit)@SOT-23 [CX1041] 93AA56A(08bit)@TSSOP8 [CX1059]  
93AA56B(16bit) [CX0001] 93AA56B(16bit)@DFN8 [CX0001]  
93AA56B(16bit)@MSOP8 [CX1015] 93AA56B(16bit)@SOIC8 [CX1045]  
93AA56B(16bit)@SOT-23 [CX1041] 93AA56B(16bit)@TSSOP8 [CX1059]  
93AA56C(08bit) [CX0001] 93AA56C(08bit)@DFN8 [CX0001]  
93AA56C(08bit)@MSOP8 [CX1015] 93AA56C(08bit)@SOIC8 [CX1045]  
93AA56C(08bit)@TSSOP8 [CX1059] 93AA56C(16bit) [CX0001]  
93AA56C(16bit)@DFN8 [CX0001] 93AA56C(16bit)@MSOP8 [CX1015]  
93AA56C(16bit)@SOIC8 [CX1045] 93AA56C(16bit)@TSSOP8 [CX1059]  
93AA66(08bit) [CX0001] 93AA66(08bit)@SOIC8 [CX1045]  
93AA66(16bit) [CX0001] 93AA66(16bit)@SOIC8 [CX1045]  
93AA66A(08bit) [CX0001] 93AA66A(08bit)@DFN8 [CX0001]  
93AA66A(08bit)@MSOP8 [CX1015] 93AA66A(08bit)@SOIC8 [CX1045]  
93AA66A(08bit)@SOT-23 [CX1041] 93AA66A(08bit)@TSSOP8 [CX1059]  
93AA66B(16bit) [CX0001] 93AA66B(16bit)@DFN8 [CX0001]  
93AA66B(16bit)@MSOP8 [CX1015] 93AA66B(16bit)@SOIC8 [CX1045]  
93AA66B(16bit)@SOT-23 [CX1041] 93AA66B(16bit)@TSSOP8 [CX1059]  
93AA66C(08bit) [CX0001] 93AA66C(08bit)@DFN8 [CX0001]

93AA66C(08bit)@MSOP8 [CX1015]      93AA66C(08bit)@SOIC8 [CX1045]  
93AA66C(08bit)@TSSOP8 [CX1059]      93AA66C(16bit) [CX0001]  
93AA66C(16bit)@DFN8 [CX0001]      93AA66C(16bit)@MSOP8 [CX1015]  
93AA66C(16bit)@SOIC8 [CX1045]      93AA66C(16bit)@TSSOP8 [CX1059]  
93AA76(08bit) [CX0001]      93AA76(08bit)@SOIC8 [CX1045]  
93AA76(16bit) [CX0001]      93AA76(16bit)@SOIC8 [CX1045]  
93AA76A(08bit) [CX0001]      93AA76A(08bit)@DFN8 [CX0001]  
93AA76A(08bit)@MSOP8 [CX1015]      93AA76A(08bit)@SOIC8 [CX1045]  
93AA76A(08bit)@SOT-23 [CX1041]      93AA76A(08bit)@TSSOP8 [CX1059]  
93AA76B(16bit) [CX0001]      93AA76B(16bit)@DFN8 [CX0001]  
93AA76B(16bit)@MSOP8 [CX1015]      93AA76B(16bit)@SOIC8 [CX1045]  
93AA76B(16bit)@SOT-23 [CX1041]      93AA76B(16bit)@TSSOP8 [CX1059]  
93AA76C(08bit) [CX0001]      93AA76C(08bit)@DFN8 [CX0001]  
93AA76C(08bit)@MSOP8 [CX1015]      93AA76C(08bit)@SOIC8 [CX1045]  
93AA76C(08bit)@TSSOP8 [CX1059]      93AA76C(16bit) [CX0001]  
93AA76C(16bit)@DFN8 [CX0001]      93AA76C(16bit)@MSOP8 [CX1015]  
93AA76C(16bit)@SOIC8 [CX1045]      93AA76C(16bit)@TSSOP8 [CX1059]  
93AA86(08bit) [CX0001]      93AA86(08bit)@SOIC8 [CX1045]  
93AA86(16bit) [CX0001]      93AA86(16bit)@SOIC8 [CX1045]  
93AA86A(08bit) [CX0001]      93AA86A(08bit)@DFN8 [CX0001]  
93AA86A(08bit)@MSOP8 [CX1015]      93AA86A(08bit)@SOIC8 [CX1045]  
93AA86A(08bit)@SOT-23 [CX1041]      93AA86A(08bit)@TSSOP8 [CX1059]  
93AA86B(16bit) [CX0001]      93AA86B(16bit)@DFN8 [CX0001]  
93AA86B(16bit)@MSOP8 [CX1015]      93AA86B(16bit)@SOIC8 [CX1045]  
93AA86B(16bit)@SOT-23 [CX1041]      93AA86B(16bit)@TSSOP8 [CX1059]  
93AA86C(08bit) [CX0001]      93AA86C(08bit)@DFN8 [CX0001]  
93AA86C(08bit)@MSOP8 [CX1015]      93AA86C(08bit)@SOIC8 [CX1045]  
93AA86C(08bit)@TSSOP8 [CX1059]      93AA86C(16bit) [CX0001]  
93AA86C(16bit)@DFN8 [CX0001]      93AA86C(16bit)@MSOP8 [CX1015]  
93AA86C(16bit)@SOIC8 [CX1045]      93AA86C(16bit)@TSSOP8 [CX1059]  
93C06(08bit) [CX0001]      93C06(08bit)@SOIC8 [CX1045]  
93C06(16bit) [CX0001]      93C06(16bit)@SOIC8 [CX1045]  
93C46(08bit) [CX0001]      93C46(08bit)@SOIC8 [CX1045]  
93C46(16bit) [CX0001]      93C46(16bit)@SOIC8 [CX1045]  
93C46A(08bit) [CX0001]      93C46A(08bit)@DFN8 [CX0001]  
93C46A(08bit)@MSOP8 [CX1015]      93C46A(08bit)@SOIC8 [CX1045]  
93C46A(08bit)@SOT-23 [CX1041]      93C46A(08bit)@TSSOP8 [CX1059]  
93C46B(16bit) [CX0001]      93C46B(16bit)@DFN8 [CX0001]  
93C46B(16bit)@MSOP8 [CX1015]      93C46B(16bit)@SOIC8 [CX1045]  
93C46B(16bit)@SOT-23 [CX1041]      93C46B(16bit)@TSSOP8 [CX1059]  
93C46C(08bit) [CX0001]      93C46C(08bit)@DFN8 [CX0001]  
93C46C(08bit)@MSOP8 [CX1015]      93C46C(08bit)@SOIC8 [CX1045]  
93C46C(08bit)@TSSOP8 [CX1059]      93C46C(16bit) [CX0001]  
93C46C(16bit)@DFN8 [CX0001]      93C46C(16bit)@MSOP8 [CX1015]  
93C46C(16bit)@SOIC8 [CX1045]      93C46C(16bit)@TSSOP8 [CX1059]  
93C56(08bit) [CX0001]      93C56(08bit)@SOIC8 [CX1045]  
93C56(16bit) [CX0001]      93C56(16bit)@SOIC8 [CX1045]  
93C56A(08bit) [CX0001]      93C56A(08bit)@DFN8 [CX0001]  
93C56A(08bit)@MSOP8 [CX1015]      93C56A(08bit)@SOIC8 [CX1045]  
93C56A(08bit)@SOT-23 [CX1041]      93C56A(08bit)@TSSOP8 [CX1059]  
93C56B(16bit) [CX0001]      93C56B(16bit)@DFN8 [CX0001]  
93C56B(16bit)@MSOP8 [CX1015]      93C56B(16bit)@SOIC8 [CX1045]  
93C56B(16bit)@SOT-23 [CX1041]      93C56B(16bit)@TSSOP8 [CX1059]  
93C56C(08bit) [CX0001]      93C56C(08bit)@DFN8 [CX0001]  
93C56C(08bit)@MSOP8 [CX1015]      93C56C(08bit)@SOIC8 [CX1045]  
93C56C(08bit)@TSSOP8 [CX1059]      93C56C(16bit) [CX0001]  
93C56C(16bit)@DFN8 [CX0001]      93C56C(16bit)@MSOP8 [CX1015]  
93C56C(16bit)@SOIC8 [CX1045]      93C56C(16bit)@TSSOP8 [CX1059]  
93C66(08bit) [CX0001]      93C66(08bit)@SOIC8 [CX1045]

93C66(16bit) [CX0001] 93C66(16bit)@SOIC8 [CX1045]  
93C66A(08bit) [CX0001] 93C66A(08bit)@DFN8 [CX0001]  
93C66A(08bit)@MSOP8 [CX1015] 93C66A(08bit)@SOIC8 [CX1045]  
93C66A(08bit)@SOT-23 [CX1041] 93C66A(08bit)@TSSOP8 [CX1059]  
93C66B(16bit) [CX0001] 93C66B(16bit)@DFN8 [CX0001]  
93C66B(16bit)@MSOP8 [CX1015] 93C66B(16bit)@SOIC8 [CX1045]  
93C66B(16bit)@SOT-23 [CX1041] 93C66B(16bit)@TSSOP8 [CX1059]  
93C66C(08bit) [CX0001] 93C66C(08bit)@DFN8 [CX0001]  
93C66C(08bit)@MSOP8 [CX1015] 93C66C(08bit)@SOIC8 [CX1045]  
93C66C(08bit)@TSSOP8 [CX1059] 93C66C(16bit) [CX0001]  
93C66C(16bit)@DFN8 [CX0001] 93C66C(16bit)@MSOP8 [CX1015]  
93C66C(16bit)@SOIC8 [CX1045] 93C66C(16bit)@TSSOP8 [CX1059]  
93C76(08bit) [CX0001] 93C76(08bit)@SOIC8 [CX1045]  
93C76(16bit) [CX0001] 93C76(16bit)@SOIC8 [CX1045]  
93C76A(08bit) [CX0001] 93C76A(08bit)@DFN8 [CX0001]  
93C76A(08bit)@MSOP8 [CX1015] 93C76A(08bit)@SOIC8 [CX1045]  
93C76A(08bit)@SOT-23 [CX1041] 93C76A(08bit)@TSSOP8 [CX1059]  
93C76B(16bit) [CX0001] 93C76B(16bit)@DFN8 [CX0001]  
93C76B(16bit)@MSOP8 [CX1015] 93C76B(16bit)@SOIC8 [CX1045]  
93C76B(16bit)@SOT-23 [CX1041] 93C76B(16bit)@TSSOP8 [CX1059]  
93C76C(08bit) [CX0001] 93C76C(08bit)@DFN8 [CX0001]  
93C76C(08bit)@MSOP8 [CX1015] 93C76C(08bit)@SOIC8 [CX1045]  
93C76C(08bit)@TSSOP8 [CX1059] 93C76C(16bit) [CX0001]  
93C76C(16bit)@DFN8 [CX0001] 93C76C(16bit)@MSOP8 [CX1015]  
93C76C(16bit)@SOIC8 [CX1045] 93C76C(16bit)@TSSOP8 [CX1059]  
93C86(08bit) [CX0001] 93C86(08bit)@SOIC8 [CX1045]  
93C86(16bit) [CX0001] 93C86(16bit)@SOIC8 [CX1045]  
93C86A(08bit) [CX0001] 93C86A(08bit)@DFN8 [CX0001]  
93C86A(08bit)@MSOP8 [CX1015] 93C86A(08bit)@SOIC8 [CX1045]  
93C86A(08bit)@SOT-23 [CX1041] 93C86A(08bit)@TSSOP8 [CX1059]  
93C86B(16bit) [CX0001] 93C86B(16bit)@DFN8 [CX0001]  
93C86B(16bit)@MSOP8 [CX1015] 93C86B(16bit)@SOIC8 [CX1045]  
93C86B(16bit)@SOT-23 [CX1041] 93C86B(16bit)@TSSOP8 [CX1059]  
93C86C(08bit) [CX0001] 93C86C(08bit)@DFN8 [CX0001]  
93C86C(08bit)@MSOP8 [CX1015] 93C86C(08bit)@SOIC8 [CX1045]  
93C86C(08bit)@TSSOP8 [CX1059] 93C86C(16bit) [CX0001]  
93C86C(16bit)@DFN8 [CX0001] 93C86C(16bit)@MSOP8 [CX1015]  
93C86C(16bit)@SOIC8 [CX1045] 93C86C(16bit)@TSSOP8 [CX1059]  
93LC46(08bit) [CX0001] 93LC46(08bit)@SOIC8 [CX1045]  
93LC46(16bit) [CX0001] 93LC46(16bit)@SOIC8 [CX1045]  
93LC46A(08bit) [CX0001] 93LC46A(08bit)@DFN8 [CX0001]  
93LC46A(08bit)@MSOP8 [CX1015] 93LC46A(08bit)@SOIC8 [CX1045]  
93LC46A(08bit)@SOT-23 [CX1041] 93LC46A(08bit)@TSSOP8 [CX1059]  
93LC46B(16bit) [CX0001] 93LC46B(16bit)@DFN8 [CX0001]  
93LC46B(16bit)@MSOP8 [CX1015] 93LC46B(16bit)@SOIC8 [CX1045]  
93LC46B(16bit)@SOT-23 [CX1041] 93LC46B(16bit)@TSSOP8 [CX1059]  
93LC46BX [CX0001] 93LC46BX@SOIC8 [CX1045]  
93LC46C(08bit) [CX0001] 93LC46C(08bit)@DFN8 [CX0001]  
93LC46C(08bit)@MSOP8 [CX1015] 93LC46C(08bit)@SOIC8 [CX1045]  
93LC46C(08bit)@TSSOP8 [CX1059] 93LC46C(16bit) [CX0001]  
93LC46C(16bit)@DFN8 [CX0001] 93LC46C(16bit)@MSOP8 [CX1015]  
93LC46C(16bit)@SOIC8 [CX1045] 93LC46C(16bit)@TSSOP8 [CX1059]  
93LC56(08bit) [CX0001] 93LC56(08bit)@SOIC8 [CX1045]  
93LC56(16bit) [CX0001] 93LC56(16bit)@SOIC8 [CX1045]  
93LC56A(08bit) [CX0001] 93LC56A(08bit)@DFN8 [CX0001]  
93LC56A(08bit)@MSOP8 [CX1015] 93LC56A(08bit)@SOIC8 [CX1045]  
93LC56A(08bit)@SOT-23 [CX1041] 93LC56A(08bit)@TSSOP8 [CX1059]  
93LC56B(16bit) [CX0001] 93LC56B(16bit)@DFN8 [CX0001]  
93LC56B(16bit)@MSOP8 [CX1015] 93LC56B(16bit)@SOIC8 [CX1045]



93LC56B(16bit)@SOT-23 [CX1041]  
93LC56BX [CX0001]  
93LC56C(08bit) [CX0001]  
93LC56C(08bit)@MSOP8 [CX1015]  
93LC56C(08bit)@TSSOP8 [CX1059]  
93LC56C(16bit)@DFN8 [CX0001]  
93LC56C(16bit)@SOIC8 [CX1045]  
93LC66(08bit) [CX0001]  
93LC66(16bit) [CX0001]  
93LC66A(08bit) [CX0001]  
93LC66A(08bit)@MSOP8 [CX1015]  
93LC66A(08bit)@SOT-23 [CX1041]  
93LC66B(16bit) [CX0001]  
93LC66B(16bit)@MSOP8 [CX1015]  
93LC66B(16bit)@SOT-23 [CX1041]  
93LC66BX [CX0001]  
93LC66C(08bit) [CX0001]  
93LC66C(08bit)@MSOP8 [CX1015]  
93LC66C(08bit)@TSSOP8 [CX1059]  
93LC66C(16bit)@DFN8 [CX0001]  
93LC66C(16bit)@SOIC8 [CX1045]  
93LC76(08bit) [CX0001]  
93LC76(16bit) [CX0001]  
93LC76A(08bit) [CX0001]  
93LC76A(08bit)@MSOP8 [CX1015]  
93LC76A(08bit)@SOT-23 [CX1041]  
93LC76B(16bit) [CX0001]  
93LC76B(16bit)@MSOP8 [CX1015]  
93LC76B(16bit)@SOT-23 [CX1041]  
93LC76C(08bit) [CX0001]  
93LC76C(08bit)@MSOP8 [CX1015]  
93LC76C(08bit)@TSSOP8 [CX1059]  
93LC76C(16bit)@DFN8 [CX0001]  
93LC76C(16bit)@SOIC8 [CX1045]  
93LC86(08bit) [CX0001]  
93LC86(16bit) [CX0001]  
93LC86A(08bit) [CX0001]  
93LC86A(08bit)@MSOP8 [CX1015]  
93LC86A(08bit)@SOT-23 [CX1041]  
93LC86B(16bit) [CX0001]  
93LC86B(16bit)@MSOP8 [CX1015]  
93LC86B(16bit)@SOT-23 [CX1041]  
93LC86C(08bit) [CX0001]  
93LC86C(08bit)@MSOP8 [CX1015]  
93LC86C(08bit)@TSSOP8 [CX1059]  
93LC86C(16bit)@DFN8 [CX0001]  
93LC86C(16bit)@SOIC8 [CX1045]  
93LCS46 [CX0001]  
93LCS46@SOIC8 [CX1045]  
93LCS56@SOIC14 [CX1000]  
93LCS66 [CX0001]  
93LCS66@SOIC8 [CX1045]  
ER5911@SOIC8 [CX1045]  
HCS101SN@SOIC8 [CX1045]  
HCS200SN@SOIC8 [CX1045]  
HCS201@SOIC8 [CX1045]  
HCS300SN@SOIC8 [CX1045]  
HCS301SN@SOIC8 [CX1045]  
HCS320SN@SOIC8 [CX1045]  
93LC56B(16bit)@TSSOP8 [CX1059]  
93LC56BX@SOIC8 [CX1045]  
93LC56C(08bit)@DFN8 [CX0001]  
93LC56C(08bit)@SOIC8 [CX1045]  
93LC56C(16bit) [CX0001]  
93LC56C(16bit)@MSOP8 [CX1015]  
93LC56C(16bit)@TSSOP8 [CX1059]  
93LC66(08bit)@SOIC8 [CX1045]  
93LC66(16bit)@SOIC8 [CX1045]  
93LC66A(08bit)@DFN8 [CX0001]  
93LC66A(08bit)@SOIC8 [CX1045]  
93LC66A(08bit)@TSSOP8 [CX1059]  
93LC66B(16bit)@DFN8 [CX0001]  
93LC66B(16bit)@SOIC8 [CX1045]  
93LC66B(16bit)@TSSOP8 [CX1059]  
93LC66BX@SOIC8 [CX1045]  
93LC66C(08bit)@DFN8 [CX0001]  
93LC66C(08bit)@SOIC8 [CX1045]  
93LC66C(16bit) [CX0001]  
93LC66C(16bit)@MSOP8 [CX1015]  
93LC66C(16bit)@TSSOP8 [CX1059]  
93LC76(08bit)@SOIC8 [CX1045]  
93LC76(16bit)@SOIC8 [CX1045]  
93LC76A(08bit)@DFN8 [CX0001]  
93LC76A(08bit)@SOIC8 [CX1045]  
93LC76A(08bit)@TSSOP8 [CX1059]  
93LC76B(16bit)@DFN8 [CX0001]  
93LC76B(16bit)@SOIC8 [CX1045]  
93LC76B(16bit)@TSSOP8 [CX1059]  
93LC76C(08bit)@DFN8 [CX0001]  
93LC76C(08bit)@SOIC8 [CX1045]  
93LC76C(16bit) [CX0001]  
93LC76C(16bit)@MSOP8 [CX1015]  
93LC76C(16bit)@TSSOP8 [CX1059]  
93LC86(08bit)@SOIC8 [CX1045]  
93LC86(16bit)@SOIC8 [CX1045]  
93LC86A(08bit)@DFN8 [CX0001]  
93LC86A(08bit)@SOIC8 [CX1045]  
93LC86A(08bit)@TSSOP8 [CX1059]  
93LC86B(16bit)@DFN8 [CX0001]  
93LC86B(16bit)@SOIC8 [CX1045]  
93LC86B(16bit)@TSSOP8 [CX1059]  
93LC86C(08bit)@DFN8 [CX0001]  
93LC86C(08bit)@SOIC8 [CX1045]  
93LC86C(16bit) [CX0001]  
93LC86C(16bit)@MSOP8 [CX1015]  
93LC86C(16bit)@TSSOP8 [CX1059]  
93LCS46@SOIC14 [CX1000]  
93LCS56 [CX0001]  
93LCS56@SOIC8 [CX1045]  
93LCS66@SOIC14 [CX1000]  
ER5911 [CX0001]  
HCS101 [CX0001]  
HCS200 [CX0001]  
HCS201 [CX0001]  
HCS300 [CX0001]  
HCS301 [CX0001]  
HCS320 [CX0001]  
HCS360 [CX0001]

HCS360SN@SOIC8 [CX1045]	HCS361 [CX0001]
HCS361SN@SOIC8 [CX1045]	HCS362 [CX0001]
HCS362@SOIC8 [CX1045]	HCS362@TSSOP8 [CX1059]
HCS410 [CX0001]	HCS410@SOIC8 [CX1045]
HCS410@TSSOP8 [CX1059]	HCS412 [CX0001]
HCS412@SOIC8 [CX1045]	HCS512 [CX0001]
HCS512@SOIC18 [CX1016]	MCP79510@MSOP10 [CX1015]
MCP79510@TDFN10 [CX4007]	MCP79511@MSOP10 [CX1015]
MCP79511@TDFN10 [CX4007]	MCP79512@MSOP10 [CX1015]
MCP79512@TDFN10 [CX4007]	MCP79520@MSOP10 [CX1015]
MCP79520@TDFN10 [CX4007]	MCP79521@MSOP10 [CX1015]
MCP79521@TDFN10 [CX4007]	MCP79522@MSOP10 [CX1015]
MCP79522@TDFN10 [CX4007]	MCP795B10@SOIC14 [CX1016]
MCP795B10@TSSOP14 [CX1000]	MCP795B11@SOIC14 [CX1016]
MCP795B11@TSSOP14 [CX1000]	MCP795B12@SOIC14 [CX1016]
MCP795B12@TSSOP14 [CX1000]	MCP795B20@SOIC14 [CX1016]
MCP795B20@TSSOP14 [CX1000]	MCP795B21@SOIC14 [CX1016]
MCP795B21@TSSOP14 [CX1000]	MCP795B22@SOIC14 [CX1016]
MCP795B22@TSSOP14 [CX1000]	MCP795W10@SOIC14 [CX1016]
MCP795W10@TSSOP14 [CX1000]	MCP795W11@SOIC14 [CX1016]
MCP795W11@TSSOP14 [CX1000]	MCP795W12@SOIC14 [CX1016]
MCP795W12@TSSOP14 [CX1000]	MCP795W20@SOIC14 [CX1016]
MCP795W20@TSSOP14 [CX1000]	MCP795W21@SOIC14 [CX1016]
MCP795W21@TSSOP14 [CX1000]	MCP795W22@SOIC14 [CX1016]
MCP795W22@TSSOP14 [CX1000]	MCP98242@DFN8 [CX4002]
MCP98242@TDFN8 [CX4002]	MCP98242@TSSOP8 [CX4002]
MCP98242@UDFN8 [CX4002]	MCP98243@DFN8 [CX4002]
MCP98243@TDFN8 [CX4002]	MCP98243@TSSOP8 [CX4002]
MCP98243@UDFN8 [CX4002]	SST25PF020B@SOIC8 [CX1045#1]
SST25PF020B@USON8 [CX4002#1]	SST25PF020B@WSON8 [CX4005#1]
SST25PF040B@SOIC8[150mil] [CX1045#1]	
SST25PF040B@SOIC8[200mil] [CX1044#1]	
SST25PF040B@WSON8 [CX4005#1]	
SST25PF080B@SOIC8[150mil] [CX1045#1]	
SST25PF080B@SOIC8[200mil] [CX1044#1]	
SST25PF080B@WSON8 [CX4005#1]	

## MICROCONTROLLER

CF745 [CX0001]	CF745@SOIC18 [CX1033]
CF745@SSOP20 [CX1026]	CF7645 [CX0001]
CF7645@SOIC18 [CX1033]	CF7665 [CX0001]
CF7665@SOIC18 [CX1033]	CF7685 [CX0001]
CF7685@SOIC18 [CX1033]	CF775 [CX0001]
CF775@SOIC28 [CX1033]	CF775@SSOP28 [CX1026]
dsPIC30F2010 [CX0001]	dsPIC30F2010(ISP) [CX0001]
dsPIC30F2010@SDIP28 [CX0032]	
dsPIC30F2010@SDIP28(ISP) [CX0001]	
dsPIC30F2010@SOIC28 [CX1033]	
dsPIC30F2010@SOIC28(ISP) [CX0001]	
dsPIC30F2011 [CX0001]	dsPIC30F2011(ISP) [CX0001]
dsPIC30F2011@QFN28 [CX4014]	dsPIC30F2011@QFN28(ISP) [CX0001]
dsPIC30F2011@SDIP18 [CX0032]	
dsPIC30F2011@SDIP18(ISP) [CX0001]	
dsPIC30F2011@SOIC18 [CX1033]	
dsPIC30F2011@SOIC18(ISP) [CX0001]	
dsPIC30F2012 [CX0001]	dsPIC30F2012(ISP) [CX0001]
dsPIC30F2012@QFN28 [CX4014]	dsPIC30F2012@QFN28(ISP) [CX0001]
dsPIC30F2012@SDIP28 [CX0032]	

dsPIC30F2012@SDIP28(ISP) [CX0001]  
dsPIC30F2012@SOIC28 [CX1033]  
dsPIC30F2012@SOIC28(ISP) [CX0001]  
dsPIC30F3010 [CX0001] dsPIC30F3010(ISP) [CX0001]  
dsPIC30F3010@QFN44 [CX4019] dsPIC30F3010@QFN44(ISP) [CX0001]  
dsPIC30F3010@SDIP28 [CX0032]  
dsPIC30F3010@SDIP28(ISP) [CX0001]  
dsPIC30F3010@SOIC28 [CX1033]  
dsPIC30F3010@SOIC28(ISP) [CX0001]  
dsPIC30F3011 [CX0001] dsPIC30F3011(ISP) [CX0001]  
dsPIC30F3011@QFN44 [CX4019] dsPIC30F3011@QFN44(ISP) [CX0001]  
dsPIC30F3011@QFP44 [CX3003] dsPIC30F3011@QFP44(ISP) [CX0001]  
dsPIC30F3012 [CX0001] dsPIC30F3012(ISP) [CX0001]  
dsPIC30F3012@QFN44 [CX4019] dsPIC30F3012@QFN44(ISP) [CX0001]  
dsPIC30F3012@QFP44 [CX3003] dsPIC30F3012@QFP44(ISP) [CX0001]  
dsPIC30F3012@SDIP18 [CX0032]  
dsPIC30F3012@SDIP18(ISP) [CX0001]  
dsPIC30F3012@SOIC18 [CX1033]  
dsPIC30F3012@SOIC18(ISP) [CX0001]  
dsPIC30F3013 [CX0001] dsPIC30F3013(ISP) [CX0001]  
dsPIC30F3013@QFN44 [CX4019] dsPIC30F3013@QFN44(ISP) [CX0001]  
dsPIC30F3013@QFP44 [CX3003] dsPIC30F3013@QFP44(ISP) [CX0001]  
dsPIC30F3013@SDIP28 [CX0032]  
dsPIC30F3013@SDIP28(ISP) [CX0001]  
dsPIC30F3013@SOIC28 [CX1033]  
dsPIC30F3013@SOIC28(ISP) [CX0001]  
dsPIC30F3014 [CX0001] dsPIC30F3014(ISP) [CX0001]  
dsPIC30F3014@QFN44 [CX4019] dsPIC30F3014@QFN44(ISP) [CX0001]  
dsPIC30F3014@QFP44 [CX3003] dsPIC30F3014@QFP44(ISP) [CX0001]  
dsPIC30F4011 [CX0001] dsPIC30F4011(ISP) [CX0001]  
dsPIC30F4011@QFN44 [CX4019] dsPIC30F4011@QFN44(ISP) [CX0001]  
dsPIC30F4011@QFP44 [CX3003] dsPIC30F4011@QFP44(ISP) [CX0001]  
dsPIC30F4011@QFP44(Delta) [CX3003]  
dsPIC30F4011@QFP44(ISP) [CX0001] dsPIC30F4011@QFP44(LB) [CX3003]  
dsPIC30F4011@QFP44(LB)(Delta) [CX3003]  
dsPIC30F4012 [CX0001] dsPIC30F4012(ISP) [CX0001]  
dsPIC30F4012@QFN44 [CX4019] dsPIC30F4012@QFN44(ISP) [CX0001]  
dsPIC30F4012@SDIP28 [CX0032]  
dsPIC30F4012@SDIP28(ISP) [CX0001]  
dsPIC30F4012@SOIC28 [CX1033]  
dsPIC30F4012@SOIC28(ISP) [CX0001]  
dsPIC30F4013 [CX0001] dsPIC30F4013(ISP) [CX0001]  
dsPIC30F4013@QFN44 [CX4019] dsPIC30F4013@QFN44(ISP) [CX0001]  
dsPIC30F4013@QFP44 [CX3003] dsPIC30F4013@QFP44(ISP) [CX0001]  
dsPIC30F5011@QFP64 [CX3011] dsPIC30F5011@QFP64(ISP) [CX0001]  
dsPIC30F5013@QFP80 [CX3016] dsPIC30F5013@QFP80(ISP) [CX0001]  
dsPIC30F5015@QFP64 [CX3011] dsPIC30F5015@QFP64(ISP) [CX0001]  
dsPIC30F5016@QFP80 [CX3016] dsPIC30F5016@QFP80(ISP) [CX0001]  
dsPIC30F6010@QFP80(ISP) [CX0001]  
dsPIC30F6010@TQFP80(ISP) [CX0001]  
dsPIC30F6010@TQFP80[14\*14] [CX3016]  
dsPIC30F6010@TQFP80[16\*16] [CX3017]  
dsPIC30F6010A@QFP80(ISP) [CX0001]  
dsPIC30F6010A@TQFP80(ISP) [CX0001]  
dsPIC30F6010A@TQFP80[14\*14] [CX3016]  
dsPIC30F6010A@TQFP80[16\*16] [CX3017]  
dsPIC30F6011@QFP64 [CX3011] dsPIC30F6011@QFP64(ISP) [CX0001]  
dsPIC30F6011@TQFP64 [CX3013]  
dsPIC30F6011@TQFP64(ISP) [CX0001]

dsPIC30F6011A@QFP64 [CX3011]  
dsPIC30F6011A@QFP64(ISP) [CX0001]  
dsPIC30F6011A@TQFP64 [CX3013]  
dsPIC30F6011A@TQFP64(ISP) [CX0001]  
dsPIC30F6012@QFP64 [CX3011] dsPIC30F6012@QFP64(ISP) [CX0001]  
dsPIC30F6012@TQFP64 [CX3013]  
dsPIC30F6012@TQFP64(ISP) [CX0001]  
dsPIC30F6012A@QFP64 [CX3011] dsPIC30F6012A@QFP64(ISP)  
dsPIC30F6012A@TQFP64 [CX3013] dsPIC30F6012A@TQFP64(ISP)  
dsPIC30F6013@QFP80(ISP) [CX0001]  
dsPIC30F6013@TQFP80[14\*14] [CX3016]  
dsPIC30F6013@TQFP80[16\*16] [CX3017]  
dsPIC30F6013A@QFP80 [CX3016]  
dsPIC30F6013A@QFP80(ISP) [CX0001]  
dsPIC30F6014@QFP80(ISP) [CX0001]  
dsPIC30F6014@TQFP80(ISP) [CX0001]  
dsPIC30F6014@TQFP80[14\*14] [CX3016]  
dsPIC30F6014@TQFP80[16\*16] [CX3017]  
dsPIC30F6014A@QFP80(ISP) dsPIC30F6014A@TQFP80(ISP)  
dsPIC30F6014A@TQFP80[14\*14] [CX3016]  
dsPIC30F6014A@TQFP80[16\*16] [CX3017]  
dsPIC30F6015@QFP64 [CX3011] dsPIC30F6015@QFP64(ISP) [CX0001]  
dsPIC33EP128GP502 [CX0001] dsPIC33EP128GP502(ISP) [CX0001]  
dsPIC33EP128GP502@QFN28 [CX4014]  
dsPIC33EP128GP502@SOIC28 [CX1033]  
dsPIC33EP128GP502@SSOP28 [CX1026]  
dsPIC33EP128GP503(ISP) [CX0001]  
dsPIC33EP128GP503@VTLA36 [CX4077]  
dsPIC33EP128GP504(ISP) [CX0001] dsPIC33EP128GP504@QFN44 [CX4019]  
dsPIC33EP128GP504@TQFP44 [CX3003#2]  
dsPIC33EP128GP504@VTLA44 [CX4079]  
dsPIC33EP128GP506(ISP) [CX0001] dsPIC33EP128GP506@QFN64 [CX4023]  
dsPIC33EP128GP506@TQFP64 [CX3011]  
dsPIC33EP128MC202 [CX0001] dsPIC33EP128MC202(ISP) [CX0001]  
dsPIC33EP128MC202@QFN28 [CX4014]  
dsPIC33EP128MC202@SOIC28 [CX1033]  
dsPIC33EP128MC202@SSOP28 [CX1026]  
dsPIC33EP128MC203(ISP) [CX0001]  
dsPIC33EP128MC203@VTLA36 [CX4077]  
dsPIC33EP128MC204(ISP) [CX0001] dsPIC33EP128MC204@QFN44 [CX4019]  
dsPIC33EP128MC204@TQFP44 [CX3003#2]  
dsPIC33EP128MC204@VTLA44 [CX4079]  
dsPIC33EP128MC206(ISP) [CX0001] dsPIC33EP128MC206@QFN64 [CX4023]  
dsPIC33EP128MC206@TQFP64 [CX3011]  
dsPIC33EP128MC502 [CX0001] dsPIC33EP128MC502(ISP) [CX0001]  
dsPIC33EP128MC502@QFN28 [CX4014]  
dsPIC33EP128MC502@SOIC28 [CX1033]  
dsPIC33EP128MC502@SSOP28 [CX1026]  
dsPIC33EP128MC503(ISP) [CX0001]  
dsPIC33EP128MC503@VTLA36 [CX4077]  
dsPIC33EP128MC504(ISP) [CX0001] dsPIC33EP128MC504@QFN44 [CX4019]  
dsPIC33EP128MC504@TQFP44 [CX3003#2]  
dsPIC33EP128MC504@VTLA44 [CX4079]  
dsPIC33EP128MC506(ISP) [CX0001] dsPIC33EP128MC506@QFN64 [CX4023]  
dsPIC33EP128MC506@TQFP64 [CX3011]  
dsPIC33EP256GP502 [CX0001] dsPIC33EP256GP502(ISP) [CX0001]  
dsPIC33EP256GP502@QFN28 [CX4014]  
dsPIC33EP256GP502@SOIC28 [CX1033]  
dsPIC33EP256GP502@SSOP28 [CX1026]

dsPIC33EP256GP503(ISP) [CX0001]  
dsPIC33EP256GP503@VTLA36 [CX4077]  
dsPIC33EP256GP504(ISP) [CX0001] dsPIC33EP256GP504@QFN44 [CX4019]  
dsPIC33EP256GP504@TQFP44 [CX3003#2]  
dsPIC33EP256GP504@VTLA44 [CX4079]  
dsPIC33EP256GP506(ISP) [CX0001] dsPIC33EP256GP506@QFN64 [CX4023]  
dsPIC33EP256GP506@TQFP64 [CX3011]  
dsPIC33EP256MC202 [CX0001] dsPIC33EP256MC202(ISP) [CX0001]  
dsPIC33EP256MC202@QFN28 [CX4014]  
dsPIC33EP256MC202@SOIC28 [CX1033]  
dsPIC33EP256MC202@SSOP28 [CX1026]  
dsPIC33EP256MC203(ISP) [CX0001]  
dsPIC33EP256MC203@VTLA36 [CX4077]  
dsPIC33EP256MC204(ISP) [CX0001] dsPIC33EP256MC204@QFN44 [CX4019]  
dsPIC33EP256MC204@TQFP44 [CX3003#2]  
dsPIC33EP256MC204@VTLA44 [CX4079]  
dsPIC33EP256MC206(ISP) [CX0001] dsPIC33EP256MC206@QFN64 [CX4023]  
dsPIC33EP256MC206@TQFP64 [CX3011]  
dsPIC33EP256MC502 [CX0001] dsPIC33EP256MC502(ISP) [CX0001]  
dsPIC33EP256MC502@QFN28 [CX4014]  
dsPIC33EP256MC502@SOIC28 [CX1033]  
dsPIC33EP256MC502@SSOP28 [CX1026]  
dsPIC33EP256MC503(ISP) [CX0001]  
dsPIC33EP256MC503@VTLA36 [CX4077]  
dsPIC33EP256MC504(ISP) [CX0001] dsPIC33EP256MC504@QFN44 [CX4019]  
dsPIC33EP256MC504@TQFP44 [CX3003#2]  
dsPIC33EP256MC504@VTLA44 [CX4079]  
dsPIC33EP256MC506(ISP) [CX0001] dsPIC33EP256MC506@QFN64 [CX4023]  
dsPIC33EP256MC506@TQFP64 [CX3011]  
dsPIC33EP32GP502 [CX0001] dsPIC33EP32GP502(ISP) [CX0001]  
dsPIC33EP32GP502@QFN28 [CX4014] dsPIC33EP32GP502@SOIC28 [CX1033]  
dsPIC33EP32GP502@SSOP28 [CX1026] dsPIC33EP32GP503(ISP) [CX0001]  
dsPIC33EP32GP503@VTLA36 [CX4077] dsPIC33EP32GP504(ISP) [CX0001]  
dsPIC33EP32GP504@QFN44 [CX4019] dsPIC33EP32GP504@TQFP44 [CX3003]  
dsPIC33EP32GP504@VTLA44 [CX4078] dsPIC33EP32MC202 [CX0001]  
dsPIC33EP32MC202(ISP) [CX0001] dsPIC33EP32MC202@QFN28 [CX4014]  
dsPIC33EP32MC202@SOIC28 [CX1033] dsPIC33EP32MC202@SSOP28 [CX1026]  
dsPIC33EP32MC203(ISP) [CX0001] dsPIC33EP32MC203@VTLA36 [CX4077]  
dsPIC33EP32MC204(ISP) [CX0001] dsPIC33EP32MC204@QFN44 [CX4019]  
dsPIC33EP32MC204@TQFP44 [CX3003] dsPIC33EP32MC204@VTLA44 [CX4078]  
dsPIC33EP32MC502 [CX0001] dsPIC33EP32MC502(ISP) [CX0001]  
dsPIC33EP32MC502@QFN28 [CX4014] dsPIC33EP32MC502@SOIC28 [CX1033]  
dsPIC33EP32MC502@SSOP28 [CX1026] dsPIC33EP32MC503(ISP) [CX0001]  
dsPIC33EP32MC503@VTLA36 [CX4077] dsPIC33EP32MC504(ISP) [CX0001]  
dsPIC33EP32MC504@QFN44 [CX4019] dsPIC33EP32MC504@TQFP44 [CX3003]  
dsPIC33EP32MC504@VTLA44 [CX4078] dsPIC33EP512GP502 [CX0001]  
dsPIC33EP512GP502(ISP) [CX0001] dsPIC33EP512GP502@QFN28 [CX4014]  
dsPIC33EP512GP502@SOIC28 [CX1033]  
dsPIC33EP512GP504(ISP) [CX0001] dsPIC33EP512GP504@QFN44 [CX4019]  
dsPIC33EP512GP504@TQFP44 [CX3003#2]  
dsPIC33EP512GP506(ISP) [CX0001] dsPIC33EP512GP506@QFN64 [CX4023]  
dsPIC33EP512GP506@TQFP64 [CX3011]  
dsPIC33EP512MC202 [CX0001] dsPIC33EP512MC202(ISP) [CX0001]  
dsPIC33EP512MC202@QFN28 [CX4014]  
dsPIC33EP512MC202@SOIC28 [CX1033]  
dsPIC33EP512MC204(ISP) [CX0001] dsPIC33EP512MC204@QFN44 [CX4019]  
dsPIC33EP512MC204@TQFP44 [CX3003#2]  
dsPIC33EP512MC206(ISP) [CX0001] dsPIC33EP512MC206@QFN64 [CX4023]  
dsPIC33EP512MC206@TQFP64 [CX3011]

dsPIC33EP512MC502 [CX0001] dsPIC33EP512MC502(ISP) [CX0001]  
dsPIC33EP512MC502@QFN28 [CX4014]  
dsPIC33EP512MC502@SOIC28 [CX1033]  
dsPIC33EP512MC504(ISP) [CX0001] dsPIC33EP512MC504@QFN44 [CX4019]  
dsPIC33EP512MC504@TQFP44 [CX3003#2]  
dsPIC33EP512MC506(ISP) [CX0001] dsPIC33EP512MC506@QFN64 [CX4023]  
dsPIC33EP512MC506@TQFP64 [CX3011]  
dsPIC33EP64GP502 [CX0001] dsPIC33EP64GP502(ISP) [CX0001]  
dsPIC33EP64GP502@QFN28 [CX4014] dsPIC33EP64GP502@SOIC28 [CX1033]  
dsPIC33EP64GP502@SSOP28 [CX1026] dsPIC33EP64GP503(ISP) [CX0001]  
dsPIC33EP64GP503@VTLA36 [CX4077] dsPIC33EP64GP504(ISP) [CX0001]  
dsPIC33EP64GP504@QFN44 [CX4019] dsPIC33EP64GP504@TQFP44 [CX3003]  
dsPIC33EP64GP506(ISP) [CX0001] dsPIC33EP64GP506@QFN64 [CX4023]  
dsPIC33EP64GP506@TQFP64 [CX3011] dsPIC33EP64MC202 [CX0001]  
dsPIC33EP64MC202(ISP) [CX0001] dsPIC33EP64MC202@QFN28 [CX4014]  
dsPIC33EP64MC202@SOIC28 [CX1033] dsPIC33EP64MC202@SSOP28 [CX1026]  
dsPIC33EP64MC203(ISP) [CX0001] dsPIC33EP64MC203@VTLA36 [CX4077]  
dsPIC33EP64MC204(ISP) [CX0001] dsPIC33EP64MC204@QFN44 [CX4019]  
dsPIC33EP64MC204@TQFP44 [CX3003] dsPIC33EP64MC206(ISP) [CX0001]  
dsPIC33EP64MC206@QFN64 [CX4023] dsPIC33EP64MC206@TQFP64 [CX3011]  
dsPIC33EP64MC502 [CX0001] dsPIC33EP64MC502(ISP) [CX0001]  
dsPIC33EP64MC502@QFN28 [CX4014] dsPIC33EP64MC502@SOIC28 [CX1033]  
dsPIC33EP64MC502@SSOP28 [CX1026] dsPIC33EP64MC503(ISP) [CX0001]  
dsPIC33EP64MC503@VTLA36 [CX4077] dsPIC33EP64MC504(ISP) [CX0001]  
dsPIC33EP64MC504@QFN44 [CX4019] dsPIC33EP64MC504@TQFP44 [CX3003]  
dsPIC33EP64MC506(ISP) [CX0001] dsPIC33EP64MC506@QFN64 [CX4023]  
dsPIC33EP64MC506@TQFP64 [CX3011] dsPIC33FJ06GS101 [CX0001]  
dsPIC33FJ06GS101(ISP) [CX0001] dsPIC33FJ06GS101@SOIC18 [CX1033]  
dsPIC33FJ06GS101@SOIC18(ISP) [CX0001]  
dsPIC33FJ06GS102 [CX0001] dsPIC33FJ06GS102(ISP) [CX0001]  
dsPIC33FJ06GS102@QFN28 [CX4014]  
dsPIC33FJ06GS102@QFN28(ISP) [CX0001]  
dsPIC33FJ06GS102@SOIC28 [CX1033]  
dsPIC33FJ06GS102@SOIC28(ISP) [CX0001]  
dsPIC33FJ06GS202 [CX0001] dsPIC33FJ06GS202(ISP) [CX0001]  
dsPIC33FJ06GS202@QFN28 [CX4014]  
dsPIC33FJ06GS202@QFN28(ISP) [CX0001]  
dsPIC33FJ06GS202@SOIC28 [CX1033]  
dsPIC33FJ06GS202@SOIC28(ISP) [CX0001]  
dsPIC33FJ128GP202 [CX0001] dsPIC33FJ128GP202(ISP) [CX0001]  
dsPIC33FJ128GP202@QFN28 [CX4032]  
dsPIC33FJ128GP202@SOIC28 [CX1033]  
dsPIC33FJ128GP204(ISP) [CX0001] dsPIC33FJ128GP204@QFN44 [CX4019]  
dsPIC33FJ128GP204@QFN44(DELTA) [CX4019]  
dsPIC33FJ128GP204@TQFP44 [CX3003]  
dsPIC33FJ128GP204@TQFP44(DELTA) [CX3003]  
dsPIC33FJ128GP206(ISP) [CX0001] dsPIC33FJ128GP206@QFN64 [CX4023]  
dsPIC33FJ128GP206@TQFP64 [CX3011]  
dsPIC33FJ128GP206A(ISP) [CX0001]  
dsPIC33FJ128GP206A@QFN64 [CX4023]  
dsPIC33FJ128GP206A@TQFP64 [CX3011]  
dsPIC33FJ128GP306(ISP) [CX0001] dsPIC33FJ128GP306@QFN64 [CX4023]  
dsPIC33FJ128GP306@TQFP64 [CX3011]  
dsPIC33FJ128GP306A(ISP) [CX0001]  
dsPIC33FJ128GP306A@QFN64 [CX4023]  
dsPIC33FJ128GP306A@TQFP64 [CX3011]  
dsPIC33FJ128GP310(ISP) [CX0001]  
dsPIC33FJ128GP310@TQFP100(1) [CX3021]  
dsPIC33FJ128GP310@TQFP100(2) [CX3071]

dsPIC33FJ128GP310A(ISP) [CX0001]  
dsPIC33FJ128GP310A@TQFP100(1) [CX3021]  
dsPIC33FJ128GP310A@TQFP100(2) [CX3071]  
dsPIC33FJ128GP706(ISP) [CX0001] dsPIC33FJ128GP706@QFN64 [CX4023]  
dsPIC33FJ128GP706@TQFP64 [CX3011]  
dsPIC33FJ128GP706A(ISP) [CX0001]  
dsPIC33FJ128GP706A@QFN64 [CX4023]  
dsPIC33FJ128GP706A@TQFP64 [CX3011]  
dsPIC33FJ128GP708(ISP) [CX0001]  
dsPIC33FJ128GP708@TQFP80 [CX3016]  
dsPIC33FJ128GP708A(ISP) [CX0001]  
dsPIC33FJ128GP708A@TQFP80 [CX3016]  
dsPIC33FJ128GP710(ISP) [CX0001]  
dsPIC33FJ128GP710@TQFP100(1) [CX3021]  
dsPIC33FJ128GP710@TQFP100(2) [CX3071]  
dsPIC33FJ128GP710A(ISP) [CX0001]  
dsPIC33FJ128GP710A@TQFP100(1) [CX3021]  
dsPIC33FJ128GP710A@TQFP100(2) [CX3071]  
dsPIC33FJ128GP802 [CX0001] dsPIC33FJ128GP802(ISP) [CX0001]  
dsPIC33FJ128GP802@QFN28 [CX4032]  
dsPIC33FJ128GP802@SOIC28 [CX1033]  
dsPIC33FJ128GP804(ISP) [CX0001] dsPIC33FJ128GP804@QFN44 [CX4019]  
dsPIC33FJ128GP804@TQFP44 [CX3003]  
dsPIC33FJ128MC202 [CX0001] dsPIC33FJ128MC202(ISP) [CX0001]  
dsPIC33FJ128MC202@QFN28 [CX4032]  
dsPIC33FJ128MC202@SOIC28 [CX1033]  
dsPIC33FJ128MC204(ISP) [CX0001] dsPIC33FJ128MC204@QFN44 [CX4019]  
dsPIC33FJ128MC204@TQFP44 [CX3003]  
dsPIC33FJ128MC506(ISP) [CX0001] dsPIC33FJ128MC506@QFN64 [CX4023]  
dsPIC33FJ128MC506@TQFP64 [CX3011]  
dsPIC33FJ128MC506A(ISP) [CX0001]  
dsPIC33FJ128MC506A@QFN64 [CX4023]  
dsPIC33FJ128MC506A@TQFP64 [CX3011]  
dsPIC33FJ128MC510(ISP) [CX0001]  
dsPIC33FJ128MC510@TQFP100(1) [CX3021]  
dsPIC33FJ128MC510@TQFP100(2) [CX3071]  
dsPIC33FJ128MC510A(ISP) [CX0001]  
dsPIC33FJ128MC510A@TQFP100(1) [CX3021]  
dsPIC33FJ128MC510A@TQFP100(2) [CX3071]  
dsPIC33FJ128MC706(ISP) [CX0001] dsPIC33FJ128MC706@QFN64 [CX4023]  
dsPIC33FJ128MC706@TQFP64 [CX3011]  
dsPIC33FJ128MC706A(ISP) [CX0001]  
dsPIC33FJ128MC706A@QFN64 [CX4023]  
dsPIC33FJ128MC706A@TQFP64 [CX3011]  
dsPIC33FJ128MC708(ISP) [CX0001]  
dsPIC33FJ128MC708@TQFP80 [CX3016]  
dsPIC33FJ128MC708A(ISP) [CX0001]  
dsPIC33FJ128MC708A@TQFP80 [CX3016]  
dsPIC33FJ128MC710(ISP) [CX0001]  
dsPIC33FJ128MC710@TQFP100(1) [CX3021]  
dsPIC33FJ128MC710@TQFP100(2) [CX3071]  
dsPIC33FJ128MC710A(ISP) [CX0001]  
dsPIC33FJ128MC710A@TQFP100(1) [CX3021]  
dsPIC33FJ128MC710A@TQFP100(2) [CX3071]  
dsPIC33FJ128MC802 [CX0001] dsPIC33FJ128MC802(ISP) [CX0001]  
dsPIC33FJ128MC802@QFN28 [CX4032]  
dsPIC33FJ128MC802@SOIC28 [CX1033]  
dsPIC33FJ128MC804(ISP) [CX0001] dsPIC33FJ128MC804@QFN44 [CX4019]  
dsPIC33FJ128MC804@TQFP44 [CX3003]

dsPIC33FJ12GP201 [CX0001] dsPIC33FJ12GP201(ISP) [CX0001]  
dsPIC33FJ12GP201@SOIC18 [CX1033]  
dsPIC33FJ12GP201@SOIC18(ISP) [CX0001]  
dsPIC33FJ12GP202 [CX0001] dsPIC33FJ12GP202(ISP) [CX0001]  
dsPIC33FJ12GP202@QFN28 [CX4014]  
dsPIC33FJ12GP202@QFN28(ISP) [CX0001]  
dsPIC33FJ12GP202@SOIC28 [CX1033]  
dsPIC33FJ12GP202@SOIC28(ISP) [CX0001]  
dsPIC33FJ12GP202@SSOP28 [CX1026]  
dsPIC33FJ12GP202@SSOP28(ISP) [CX0001]  
dsPIC33FJ12MC201 [CX0001] dsPIC33FJ12MC201(ISP) [CX0001]  
dsPIC33FJ12MC201@SOIC20 [CX1033]  
dsPIC33FJ12MC201@SOIC20(ISP) [CX0001]  
dsPIC33FJ12MC201@SSOP20 [CX1026]  
dsPIC33FJ12MC201@SSOP20(ISP) [CX0001]  
dsPIC33FJ12MC202 [CX0001] dsPIC33FJ12MC202(ISP) [CX0001]  
dsPIC33FJ12MC202@QFN28 [CX4014]  
dsPIC33FJ12MC202@QFN28(ISP) [CX0001]  
dsPIC33FJ12MC202@SOIC28 [CX1033]  
dsPIC33FJ12MC202@SOIC28(ISP) [CX0001]  
dsPIC33FJ12MC202@SSOP28 [CX1026]  
dsPIC33FJ12MC202@SSOP28(ISP) [CX0001]  
dsPIC33FJ16GP304@QFN44 [CX4019]  
dsPIC33FJ16GP304@QFN44(ISP) [CX0001]  
dsPIC33FJ16GP304@TQFP44 [CX3003]  
dsPIC33FJ16GP304@TQFP44(ISP) [CX0001]  
dsPIC33FJ16GS402 [CX0001] dsPIC33FJ16GS402(ISP) [CX0001]  
dsPIC33FJ16GS402@QFN28 [CX4014]  
dsPIC33FJ16GS402@QFN28(ISP) [CX0001]  
dsPIC33FJ16GS402@SOIC28 [CX1033]  
dsPIC33FJ16GS402@SOIC28(ISP) [CX0001]  
dsPIC33FJ16GS404@QFN44 [CX4019]  
dsPIC33FJ16GS404@QFN44(ISP) [CX0001]  
dsPIC33FJ16GS404@TQFP44 [CX3003]  
dsPIC33FJ16GS404@TQFP44(ISP) [CX0001]  
dsPIC33FJ16GS404@VLAP44 [CX4019]  
dsPIC33FJ16GS404@VLAP44(ISP) [CX0001]  
dsPIC33FJ16GS502 [CX0001] dsPIC33FJ16GS502(ISP) [CX0001]  
dsPIC33FJ16GS502@QFN28 [CX4014]  
dsPIC33FJ16GS502@QFN28(ISP) [CX0001]  
dsPIC33FJ16GS502@SOIC28 [CX1033]  
dsPIC33FJ16GS502@SOIC28(ISP) [CX0001]  
dsPIC33FJ16GS504@QFN44 [CX4019]  
dsPIC33FJ16GS504@QFN44(ISP) [CX0001]  
dsPIC33FJ16GS504@TQFP44 [CX3003]  
dsPIC33FJ16GS504@TQFP44(ISP) [CX0001]  
dsPIC33FJ16GS504@VLAP44 [CX4019]  
dsPIC33FJ16GS504@VLAP44(ISP) [CX0001]  
dsPIC33FJ16MC304@QFN44 [CX4019]  
dsPIC33FJ16MC304@QFN44(ISP) [CX0001]  
dsPIC33FJ16MC304@TQFP44 [CX3003]  
dsPIC33FJ16MC304@TQFP44(ISP) [CX0001]  
dsPIC33FJ256GP506(ISP) [CX0001] dsPIC33FJ256GP506@QFN64 [CX4023]  
dsPIC33FJ256GP506@TQFP64 [CX3011]  
dsPIC33FJ256GP506A(ISP) [CX0001]  
dsPIC33FJ256GP506A@QFN64 [CX4023]  
dsPIC33FJ256GP506A@TQFP64 [CX3011]  
dsPIC33FJ256GP510(ISP) [CX0001]  
dsPIC33FJ256GP510@TQFP100(1) [CX3021]



dsPIC33FJ256GP510@TQFP100(2) [CX3071]  
dsPIC33FJ256GP510A(ISP) [CX0001]  
dsPIC33FJ256GP510A@TQFP100(1) [CX3021]  
dsPIC33FJ256GP510A@TQFP100(2) [CX3071]  
dsPIC33FJ256GP710(ISP) [CX0001]  
dsPIC33FJ256GP710@TQFP100(1) [CX3021]  
dsPIC33FJ256GP710@TQFP100(2) [CX3071]  
dsPIC33FJ256GP710A(ISP) [CX0001]  
dsPIC33FJ256GP710A@TQFP100(1) [CX3021]  
dsPIC33FJ256GP710A@TQFP100(2) [CX3071]  
dsPIC33FJ256MC510(ISP) [CX0001]  
dsPIC33FJ256MC510@TQFP100(1) [CX3021]  
dsPIC33FJ256MC510@TQFP100(2) [CX3071]  
dsPIC33FJ256MC510A(ISP) [CX0001]  
dsPIC33FJ256MC510A@TQFP100(1) [CX3021]  
dsPIC33FJ256MC510A@TQFP100(2) [CX3071]  
dsPIC33FJ256MC710(ISP) [CX0001]  
dsPIC33FJ256MC710@TQFP100(1) [CX3021]  
dsPIC33FJ256MC710@TQFP100(2) [CX3071]  
dsPIC33FJ256MC710A(ISP) [CX0001]  
dsPIC33FJ256MC710A@TQFP100(1) [CX3021]  
dsPIC33FJ256MC710A@TQFP100(2) [CX3071]  
dsPIC33FJ32GP202 [CX0001] dsPIC33FJ32GP202(ISP) [CX0001]  
dsPIC33FJ32GP202@QFN28 [CX4014]  
dsPIC33FJ32GP202@QFN28(ISP) [CX0001]  
dsPIC33FJ32GP202@SOIC28 [CX1033]  
dsPIC33FJ32GP202@SOIC28(ISP) [CX0001]  
dsPIC33FJ32GP204@QFN44 [CX4019]  
dsPIC33FJ32GP204@QFN44(ISP) [CX0001]  
dsPIC33FJ32GP204@TQFP44 [CX3003]  
dsPIC33FJ32GP204@TQFP44(ISP) [CX0001]  
dsPIC33FJ32GP302 [CX0001] dsPIC33FJ32GP302(ISP) [CX0001]  
dsPIC33FJ32GP302@QFN28 [CX4014]  
dsPIC33FJ32GP302@QFN28(ISP) [CX0001]  
dsPIC33FJ32GP302@SOIC28 [CX1033]  
dsPIC33FJ32GP302@SOIC28(ISP) [CX0001]  
dsPIC33FJ32GP304@QFN44 [CX4019]  
dsPIC33FJ32GP304@QFN44(ISP) [CX0001]  
dsPIC33FJ32GP304@TQFP44 [CX3003]  
dsPIC33FJ32GP304@TQFP44(ISP) [CX0001]  
dsPIC33FJ32GS406@QFN64 [CX4023]  
dsPIC33FJ32GS406@QFN64(ISP) [CX0001]  
dsPIC33FJ32GS406@TQFP64 [CX3011]  
dsPIC33FJ32GS406@TQFP64(ISP) [CX0001]  
dsPIC33FJ32GS606@QFN64 [CX4023]  
dsPIC33FJ32GS606@QFN64(ISP) [CX0001]  
dsPIC33FJ32GS606@TQFP64 [CX3011]  
dsPIC33FJ32GS606@TQFP64(ISP) [CX0001]  
dsPIC33FJ32GS608@TQFP80 [CX3016]  
dsPIC33FJ32GS608@TQFP80(ISP) [CX0001]  
dsPIC33FJ32GS610@TQFP100(1) [CX3021]  
dsPIC33FJ32GS610@TQFP100(1)(ISP) [CX0001]  
dsPIC33FJ32GS610@TQFP100(2) [CX3071]  
dsPIC33FJ32GS610@TQFP100(2)(ISP) [CX0001]  
dsPIC33FJ32MC202 [CX0001] dsPIC33FJ32MC202(ISP) [CX0001]  
dsPIC33FJ32MC202@QFN28 [CX4014]  
dsPIC33FJ32MC202@QFN28(ISP) [CX0001]  
dsPIC33FJ32MC202@SOIC28 [CX1033]  
dsPIC33FJ32MC202@SOIC28(ISP) [CX0001]

dsPIC33FJ32MC204@QFN44 [CX4019]  
dsPIC33FJ32MC204@QFN44(ISP) [CX0001]  
dsPIC33FJ32MC204@TQFP44 [CX3003]  
dsPIC33FJ32MC204@TQFP44(ISP) [CX0001]  
dsPIC33FJ32MC302 [CX0001] dsPIC33FJ32MC302(ISP) [CX0001]  
dsPIC33FJ32MC302@QFN28 [CX4014]  
dsPIC33FJ32MC302@QFN28(ISP) [CX0001]  
dsPIC33FJ32MC302@SOIC28 [CX1033]  
dsPIC33FJ32MC302@SOIC28(ISP) [CX0001]  
dsPIC33FJ32MC304@QFN44 [CX4019]  
dsPIC33FJ32MC304@QFN44(ISP) [CX0001]  
dsPIC33FJ32MC304@TQFP44 [CX3003]  
dsPIC33FJ32MC304@TQFP44(ISP) [CX0001]  
dsPIC33FJ64GP202 [CX0001] dsPIC33FJ64GP202(ISP) [CX0001]  
dsPIC33FJ64GP202@QFN28 [CX4014]  
dsPIC33FJ64GP202@QFN28(ISP) [CX0001]  
dsPIC33FJ64GP202@SOIC28 [CX1033]  
dsPIC33FJ64GP202@SOIC28(ISP) [CX0001]  
dsPIC33FJ64GP204@QFN44 [CX4019]  
dsPIC33FJ64GP204@QFN44(ISP) [CX0001]  
dsPIC33FJ64GP204@TQFP44 [CX3003]  
dsPIC33FJ64GP204@TQFP44(ISP) [CX0001]  
dsPIC33FJ64GP206@QFN64 [CX4023]  
dsPIC33FJ64GP206@QFN64(ISP) [CX0001]  
dsPIC33FJ64GP206@TQFP64 [CX3011]  
dsPIC33FJ64GP206@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GP206A@QFN64 [CX4023]  
dsPIC33FJ64GP206A@QFN64(ISP) [CX0001]  
dsPIC33FJ64GP206A@TQFP64 [CX3011]  
dsPIC33FJ64GP206A@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GP306@QFN64 [CX4023]  
dsPIC33FJ64GP306@QFN64(ISP) [CX0001]  
dsPIC33FJ64GP306@TQFP64 [CX3011]  
dsPIC33FJ64GP306@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GP306A@QFN64 [CX4023]  
dsPIC33FJ64GP306A@QFN64(ISP) [CX0001]  
dsPIC33FJ64GP306A@TQFP64 [CX3011]  
dsPIC33FJ64GP306A@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GP310@TQFP100(1) [CX3021]  
dsPIC33FJ64GP310@TQFP100(1)(ISP) [CX0001]  
dsPIC33FJ64GP310@TQFP100(2) [CX3071]  
dsPIC33FJ64GP310@TQFP100(2)(ISP) [CX0001]  
dsPIC33FJ64GP310A@TQFP100(1) [CX3021]  
dsPIC33FJ64GP310A@TQFP100(1)ISP [CX0001]  
dsPIC33FJ64GP310A@TQFP100(2) [CX3071]  
dsPIC33FJ64GP310A@TQFP100(2)ISP [CX0001]  
dsPIC33FJ64GP706@QFN64 [CX4023]  
dsPIC33FJ64GP706@QFN64(ISP) [CX0001]  
dsPIC33FJ64GP706@TQFP64 [CX3011]  
dsPIC33FJ64GP706@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GP706A@QFN64 [CX4023]  
dsPIC33FJ64GP706A@QFN64(ISP) [CX0001]  
dsPIC33FJ64GP706A@TQFP64 [CX3011]  
dsPIC33FJ64GP706A@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GP708@TQFP80 [CX3016]  
dsPIC33FJ64GP708@TQFP80(ISP) [CX0001]  
dsPIC33FJ64GP708A@TQFP80 [CX3016]  
dsPIC33FJ64GP708A@TQFP80(ISP) [CX0001]  
dsPIC33FJ64GP710@TQFP100(1) [CX3021]

dsPIC33FJ64GP710@TQFP100(1)(ISP) [CX0001]  
dsPIC33FJ64GP710@TQFP100(2) [CX3071]  
dsPIC33FJ64GP710@TQFP100(2)(ISP) [CX0001]  
dsPIC33FJ64GP710A@TQFP100(1) [CX3021]  
dsPIC33FJ64GP710A@TQFP100(1)ISP [CX0001]  
dsPIC33FJ64GP710A@TQFP100(2) [CX3071]  
dsPIC33FJ64GP710A@TQFP100(2)ISP [CX0001]  
dsPIC33FJ64GP802 [CX0001] dsPIC33FJ64GP802(ISP) [CX0001]  
dsPIC33FJ64GP802@QFN28 [CX4014]  
dsPIC33FJ64GP802@QFN28(ISP) [CX0001]  
dsPIC33FJ64GP802@SOIC28 [CX1033]  
dsPIC33FJ64GP802@SOIC28(ISP) [CX0001]  
dsPIC33FJ64GP804@QFN44 [CX4019]  
dsPIC33FJ64GP804@QFN44(ISP) [CX0001]  
dsPIC33FJ64GP804@TQFP44 [CX3003]  
dsPIC33FJ64GP804@TQFP44(ISP) [CX0001]  
dsPIC33FJ64GS406@QFN64 [CX4023]  
dsPIC33FJ64GS406@QFN64(ISP) [CX0001]  
dsPIC33FJ64GS406@TQFP64 [CX3011]  
dsPIC33FJ64GS406@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GS606@QFN64 [CX4023]  
dsPIC33FJ64GS606@QFN64(ISP) [CX0001]  
dsPIC33FJ64GS606@TQFP64 [CX3011]  
dsPIC33FJ64GS606@TQFP64(ISP) [CX0001]  
dsPIC33FJ64GS608@TQFP80 [CX3016]  
dsPIC33FJ64GS608@TQFP80(ISP) [CX0001]  
dsPIC33FJ64GS610@TQFP100(1) [CX3021]  
dsPIC33FJ64GS610@TQFP100(1)(ISP) [CX0001]  
dsPIC33FJ64GS610@TQFP100(2) [CX3071]  
dsPIC33FJ64GS610@TQFP100(2)(ISP) [CX0001]  
dsPIC33FJ64MC202 [CX0001] dsPIC33FJ64MC202(ISP) [CX0001]  
dsPIC33FJ64MC202@QFN28 [CX4014]  
dsPIC33FJ64MC202@QFN28(ISP) [CX0001]  
dsPIC33FJ64MC202@SOIC28 [CX1033]  
dsPIC33FJ64MC202@SOIC28(ISP) [CX0001]  
dsPIC33FJ64MC204@QFN44 [CX4019]  
dsPIC33FJ64MC204@QFN44(ISP) [CX0001]  
dsPIC33FJ64MC204@TQFP44 [CX3003]  
dsPIC33FJ64MC204@TQFP44(ISP) [CX0001]  
dsPIC33FJ64MC506@QFN64 [CX4023]  
dsPIC33FJ64MC506@QFN64(ISP) [CX0001]  
dsPIC33FJ64MC506@TQFP64 [CX3011]  
dsPIC33FJ64MC506@TQFP64(ISP) [CX0001]  
dsPIC33FJ64MC506A@QFN64 [CX4023]  
dsPIC33FJ64MC506A@QFN64(ISP) [CX0001]  
dsPIC33FJ64MC506A@TQFP64 [CX3011]  
dsPIC33FJ64MC506A@TQFP64(ISP) [CX0001]  
dsPIC33FJ64MC508@TQFP80 [CX3016]  
dsPIC33FJ64MC508@TQFP80(ISP) [CX0001]  
dsPIC33FJ64MC508A@TQFP80 [CX3016]  
dsPIC33FJ64MC508A@TQFP80(ISP) [CX0001]  
dsPIC33FJ64MC510@TQFP100(1) [CX3021]  
dsPIC33FJ64MC510@TQFP100(1)(ISP) [CX0001]  
dsPIC33FJ64MC510@TQFP100(2) [CX3071]  
dsPIC33FJ64MC510@TQFP100(2)(ISP) [CX0001]  
dsPIC33FJ64MC510A@TQFP100(1) [CX3021]  
dsPIC33FJ64MC510A@TQFP100(1)ISP [CX0001]  
dsPIC33FJ64MC510A@TQFP100(2) [CX3071]  
dsPIC33FJ64MC510A@TQFP100(2)ISP [CX0001]

dsPIC33FJ64MC706@QFN64 [CX4023]  
dsPIC33FJ64MC706@QFN64(ISP) [CX0001]  
dsPIC33FJ64MC706@TQFP64 [CX3011]  
dsPIC33FJ64MC706@TQFP64(ISP) [CX0001]  
dsPIC33FJ64MC706A@QFN64 [CX4023]  
dsPIC33FJ64MC706A@QFN64(ISP) [CX0001]  
dsPIC33FJ64MC706A@TQFP64 [CX3011]  
dsPIC33FJ64MC706A@TQFP64(ISP) [CX0001]  
dsPIC33FJ64MC710@TQFP100(1) [CX3021]  
dsPIC33FJ64MC710@TQFP100(1)(ISP) [CX0001]  
dsPIC33FJ64MC710@TQFP100(2) [CX3071]  
dsPIC33FJ64MC710@TQFP100(2)(ISP) [CX0001]  
dsPIC33FJ64MC710A@TQFP100(1) [CX3021]  
dsPIC33FJ64MC710A@TQFP100(1)ISP [CX0001]  
dsPIC33FJ64MC710A@TQFP100(2) [CX3071]  
dsPIC33FJ64MC710A@TQFP100(2)ISP [CX0001]  
dsPIC33FJ64MC802 [CX0001] dsPIC33FJ64MC802(ISP) [CX0001]  
dsPIC33FJ64MC802@QFN28 [CX4014]  
dsPIC33FJ64MC802@QFN28(ISP) [CX0001]  
dsPIC33FJ64MC802@SOIC28 [CX1033]  
dsPIC33FJ64MC802@SOIC28(ISP) [CX0001]  
dsPIC33FJ64MC804@QFN44 [CX4019]  
dsPIC33FJ64MC804@QFN44(ISP) [CX0001]  
dsPIC33FJ64MC804@TQFP44 [CX3003]  
dsPIC33FJ64MC804@TQFP44(ISP) [CX0001]  
HA2089 [CX0001] HA2089@QFN16 [CX4010]  
HA2089@SOIC14 [CX1065] HA2089@TSSOP14 [CX1000]  
HA2099 [CX0001] HA2099@SOIC18 [CX1033]  
HA2099@SSOP20 [CX1026] HA3089 [CX0001]  
HA3089@QFN28 [CX4014] HA3089@SOIC28 [CX1033]  
HA3089@SSOP28 [CX1026] HA3099 [CX0001]  
HA3099@QFN28 [CX4014] HA3099@SOIC28 [CX1033]  
HA3099@SSOP28 [CX1026] MCP25020 [CX0001]  
MCP25020(ISP) [CX0001] MCP25020@SOIC14 [CX1033]  
MCP25020@SOIC14(ISP) [CX0001] MCP25020@TSSOP14 [CX1016]  
MCP25020@TSSOP14(ISP) [CX0001] MCP25025 [CX0001]  
MCP25025(ISP) [CX0001] MCP25025@SOIC14 [CX1033]  
MCP25025@SOIC14(ISP) [CX0001] MCP25025@TSSOP14 [CX1016]  
MCP25025@TSSOP14(ISP) [CX0001] MCP25050 [CX0001]  
MCP25050(ISP) [CX0001] MCP25050@SOIC14 [CX1033]  
MCP25050@SOIC14(ISP) [CX0001] MCP25050@TSSOP14 [CX1016]  
MCP25050@TSSOP14(ISP) [CX0001] MCP25055 [CX0001]  
MCP25055(ISP) [CX0001] MCP25055@SOIC14 [CX1033]  
MCP25055@SOIC14(ISP) [CX0001] MCP25055@TSSOP14 [CX1016]  
MCP25055@TSSOP14(ISP) [CX0001] MCV08A [CX0001]  
MCV08A@MSOP8 [CX1015] MCV08A@SOIC8[150mil] [CX1045]  
MCV08A@SOIC8[200mil] [CX1044] MCV14A [CX0001]  
MCV14A@SOIC14 [CX1016] MCV14A@TSSOP14 [CX1000]  
MCV18A [CX0001] MCV18A@SOIC18 [CX1033]  
MCV18A@SSOP20 [CX1026] MCV28A [CX0001]  
MCV28A@SOIC28 [CX1033] MCV28A@SSOP28 [CX1026]  
PIC10F200 [CX0001] PIC10F200(ISP) [CX0001]  
PIC10F200@DFN8 [CX4002] PIC10F200@SOT6 [CX1041]  
PIC10F200@SOT6(ISP) [CX0001] PIC10F202 [CX0001]  
PIC10F202(ISP) [CX0001] PIC10F202@DFN8 [CX4002]  
PIC10F202@SOT6 [CX1041] PIC10F202@SOT6(ISP) [CX0001]  
PIC10F204 [CX0001] PIC10F204(ISP) [CX0001]  
PIC10F204@DFN8 [CX4002] PIC10F204@SOT6 [CX1041]  
PIC10F204@SOT6(ISP) [CX0001] PIC10F206 [CX0001]

PIC10F206(ISP) [CX0001] PIC10F206@DFN8 [CX4002]  
PIC10F206@SOT6 [CX1041] PIC10F206@SOT6(ISP) [CX0001]  
PIC10F220 [CX0001] PIC10F220(ISP) [CX0001]  
PIC10F220@DFN8 [CX4002] PIC10F220@SOT6 [CX1041]  
PIC10F220@SOT6(ISP) [CX0001] PIC10F222 [CX0001]  
PIC10F222(ISP) [CX0001] PIC10F222@DFN8 [CX4002]  
PIC10F222@SOT6 [CX1041] PIC10F222@SOT6(ISP) [CX0001]  
PIC10F320 [CX0001] PIC10F320(32 WORD PRO) [CX0001]  
PIC10F320(32 WORD PRO)(ISP) [CX0001]  
PIC10F320(32 WORD PRO)@DFN8 [CX4002]  
PIC10F320(32 WORD PRO)@SOT-23 [CX1041]  
PIC10F320(ISP) [CX0001] PIC10F320@DFN8 [CX4002]  
PIC10F320@SOT-23 [CX1041] PIC10F322 [CX0001]  
PIC10F322(32 WORD PRO) [CX0001]  
PIC10F322(32 WORD PRO)(ISP) [CX0001]  
PIC10F322(32 WORD PRO)@DFN8 [CX4002]  
PIC10F322(32 WORD PRO)@SOT-23 [CX1041]  
PIC10F322(ISP) [CX0001] PIC10F322@DFN8 [CX4002]  
PIC10F322@SOT-23 [CX1041] PIC10LF320 [CX0001]  
PIC10LF320(32 WORD PRO) [CX0001]  
PIC10LF320(32 WORD PRO)(ISP) [CX0001]  
PIC10LF320(32 WORD PRO)@DFN8 [CX4002]  
PIC10LF320(32 WORD PRO)@SOT-23 [CX1041]  
PIC10LF320(ISP) [CX0001] PIC10LF320@DFN8 [CX4002]  
PIC10LF320@SOT-23 [CX1041] PIC10LF322 [CX0001]  
PIC10LF322(32 WORD PRO) [CX0001]  
PIC10LF322(32 WORD PRO)(ISP) [CX0001]  
PIC10LF322(32 WORD PRO)@DFN8 [CX4002]  
PIC10LF322(32 WORD PRO)@SOT-23 [CX1041]  
PIC10LF322(ISP) [CX0001] PIC10LF322@DFN8 [CX4002]  
PIC10LF322@SOT-23 [CX1041] PIC12C508 [CX0001]  
PIC12C508(ISP) [CX0001] PIC12C508@SOIC8 [CX1032]  
PIC12C508@SOIC8(ISP) [CX0001] PIC12C508A [CX0001]  
PIC12C508A(ISP) [CX0001] PIC12C508A(SM)@SOIC8 [CX1032]  
PIC12C508A(SM)@SOIC8(ISP) [CX0001]  
PIC12C508A(SN)@SOIC8 [CX1016]  
PIC12C508A(SN)@SOIC8(ISP) [CX0001]  
PIC12C509 [CX0001] PIC12C509(ISP) [CX0001]  
PIC12C509(SM)@SOIC8 [CX1032]  
PIC12C509(SM)@SOIC8(ISP) [CX0001]  
PIC12C509(SN)@SOIC8 [CX1016]  
PIC12C509(SN)@SOIC8(ISP) [CX0001]  
PIC12C509A [CX0001] PIC12C509A(ISP) [CX0001]  
PIC12C509A(SM)@SOIC8 [CX1032]  
PIC12C509A(SM)@SOIC8(ISP) [CX0001]  
PIC12C509A(SN)@SOIC8 [CX1016]  
PIC12C509A(SN)@SOIC8(ISP) [CX0001]  
PIC12C509A@DFN8 [CX4005] PIC12C509A@DFN8(ISP) [CX0001]  
PIC12C671 [CX0001] PIC12C671(ISP) [CX0001]  
PIC12C671@DFN8 [CX4005] PIC12C671@DFN8(ISP) [CX0001]  
PIC12C671@SOIC8 [CX1044] PIC12C671@SOIC8(ISP) [CX0001]  
PIC12C672 [CX0001] PIC12C672(ISP) [CX0001]  
PIC12C672@DFN8 [CX4005] PIC12C672@DFN8(ISP) [CX0001]  
PIC12C672@SOIC8 [CX1044] PIC12C672@SOIC8(ISP) [CX0001]  
PIC12CE518 [CX0001] PIC12CE518(ISP) [CX0001]  
PIC12CE518@SOIC8 [CX1032] PIC12CE518@SOIC8(ISP) [CX0001]  
PIC12CE519 [CX0001] PIC12CE519(ISP) [CX0001]  
PIC12CE519(SM)@SOIC8 [CX1032]  
PIC12CE519(SM)@SOIC8(ISP) [CX0001]

PIC12CE519(SN)@SOIC8 [CX1016]  
PIC12CE519(SN)@SOIC8(ISP) [CX0001]  
PIC12CE673 [CX0001]  
PIC12CE673@SOIC8 [CX1044]  
PIC12CE674 [CX0001]  
PIC12CE674@SOIC8 [CX1044]  
PIC12F1501 [CX0001]  
PIC12F1501(MC)@DFN8 [CX4002]  
PIC12F1501@DFN8(ISP) [CX0001]  
PIC12F1501@MSOP8(ISP) [CX0001]  
PIC12F1501@SOIC8(ISP) [CX0001]  
PIC12F1822(8-word) [CX0001]  
PIC12F1822(LV) [CX0001]  
PIC12F1822@DFN8 [CX4003]  
PIC12F1822@DFN8(ISP)(HV) [CX0001]  
PIC12F1822@DFN8(LV) [CX4002]  
PIC12F1822@SOIC8(8-word) [CX1045]  
PIC12F1822@SOIC8(ISP)(HV) [CX0001]  
PIC12F1822@SOIC8(LV) [CX1045]  
PIC12F1840(ISP)(HV) [CX0001]  
PIC12F1840@DFN8(ISP)(HV) [CX0001]  
PIC12F1840@SOIC8 [CX1045]  
PIC12F1840@SOIC8(ISP)(HV) [CX0001]  
PIC12F1840E [CX0001]  
PIC12F1840E@SOIC8 [CX1045]  
PIC12F508(ISP) [CX0001]  
PIC12F508@MSOP8(ISP) [CX0001]  
PIC12F508@SOIC8(ISP) [CX0001]  
PIC12F509(ISP) [CX0001]  
PIC12F509@MSOP8(ISP) [CX0001]  
PIC12F509@SOIC8(ISP) [CX0001]  
PIC12F510(ISP) [CX0001]  
PIC12F510@MSOP8(ISP) [CX0001]  
PIC12F510@SOIC8(150mil)(ISP) [CX0001]  
PIC12F510@SOIC8(200mil) [CX1044]  
PIC12F510@SOIC8(200mil)(ISP) [CX0001]  
PIC12F519 [CX0001]  
PIC12F519@DFN8 [CX4002]  
PIC12F519@MSOP8 [CX1015]  
PIC12F519@SOIC8 [CX1045]  
PIC12F529T39A [CX1000]  
PIC12F529T48A [CX1000]  
PIC12F609 [CX0001]  
PIC12F609@DFN8 [CX4003]  
PIC12F609@DFN8-S [CX4005]  
PIC12F609@MSOP8 [CX1015]  
PIC12F609@SOIC8 [CX1045]  
PIC12F615 [CX0001]  
PIC12F615@DFN8 [CX4003]  
PIC12F615@DFN8-S [CX4005]  
PIC12F615@MSOP8 [CX1015]  
PIC12F615@SOIC8 [CX1045]  
PIC12F617 [CX0001]  
PIC12F617@DFN8 [CX4003]  
PIC12F617@DFN8-S [CX4005]  
PIC12F617@MSOP8 [CX1015]  
PIC12F617@SOIC8 [CX1045]  
PIC12F629 [CX0001]  
PIC12F629(SM)@SOIC8 [CX1032]  
PIC12CE673(ISP) [CX0001]  
PIC12CE673@SOIC8(ISP) [CX0001]  
PIC12CE674(ISP) [CX0001]  
PIC12CE674@SOIC8(ISP) [CX0001]  
PIC12F1501(ISP) [CX0001]  
PIC12F1501(MF)@DFN8 [CX4003]  
PIC12F1501@MSOP8 [CX1015]  
PIC12F1501@SOIC8 [CX1045]  
PIC12F1822 [CX0001]  
PIC12F1822(ISP)(HV) [CX0001]  
PIC12F1822(LVISP) [CX0001]  
PIC12F1822@DFN8(8-word) [CX4003]  
PIC12F1822@SOIC8 [CX1045]  
PIC12F1840 [CX0001]  
PIC12F1840@DFN8 [CX4003]  
PIC12F1840E@DFN8 [CX4003]  
PIC12F508 [CX0001]  
PIC12F508@MSOP8 [CX1015]  
PIC12F508@SOIC8 [CX1016]  
PIC12F509 [CX0001]  
PIC12F509@MSOP8 [CX1015]  
PIC12F509@SOIC8 [CX1016]  
PIC12F510 [CX0001]  
PIC12F510@MSOP8 [CX1015]  
PIC12F510@SOIC8(150mil) [CX1045]  
PIC12F519(ISP) [CX0001]  
PIC12F519@DFN8(ISP) [CX0001]  
PIC12F519@MSOP8(ISP) [CX0001]  
PIC12F519@SOIC8(ISP) [CX0001]  
PIC12F529T39A(ISP) [CX0001]  
PIC12F529T48A(ISP) [CX0001]  
PIC12F609(ISP) [CX0001]  
PIC12F609@DFN8(ISP) [CX0001]  
PIC12F609@DFN8-S(ISP) [CX0001]  
PIC12F609@MSOP8(ISP) [CX0001]  
PIC12F609@SOIC8(ISP) [CX0001]  
PIC12F615(ISP) [CX0001]  
PIC12F615@DFN8(ISP) [CX0001]  
PIC12F615@DFN8-S(ISP) [CX0001]  
PIC12F615@MSOP8(ISP) [CX0001]  
PIC12F615@SOIC8(ISP) [CX0001]  
PIC12F617(ISP) [CX0001]  
PIC12F617@DFN8(ISP) [CX0001]  
PIC12F617@DFN8-S(ISP) [CX0001]  
PIC12F617@MSOP8(ISP) [CX0001]  
PIC12F617@SOIC8(ISP) [CX0001]  
PIC12F629(ISP) [CX0001]

PIC12F629(SM)@SOIC8(ISP) [CX0001]  
PIC12F629(SN)@SOIC8 [CX1016]  
PIC12F629(SN)@SOIC8(ISP) [CX0001]  
PIC12F629@DFN8 [CX4005] PIC12F629@DFN8(ISP) [CX0001]  
PIC12F635 [CX0001] PIC12F635(4-WORD PRO) [CX0001]  
PIC12F635(ISP) [CX0001] PIC12F635(MD)@DFN8 [CX4004]  
PIC12F635(MD)@DFN8(4-WORD PRO) [CX4004]  
PIC12F635(MD)@DFN8(ISP) [CX0001] PIC12F635(MF)@DFN8 [CX4005]  
PIC12F635(MF)@DFN8(4-WORD PRO) [CX4005]  
PIC12F635(MF)@DFN8(ISP) [CX0001] PIC12F635(SM)@SOIC8 [CX1032]  
PIC12F635(SM)@SOIC8(4-WORD PRO) [CX1032]  
PIC12F635(SM)@SOIC8(ISP) [CX0001]  
PIC12F635(SN)@SOIC8 [CX1016]  
PIC12F635(SN)@SOIC8(4-WORD PRO) [CX1016]  
PIC12F635(SN)@SOIC8(ISP) [CX0001]  
PIC12F675 [CX0001] PIC12F675(ISP) [CX0001]  
PIC12F675(SM)@SOIC8 [CX1032]  
PIC12F675(SM)@SOIC8(ISP) [CX0001]  
PIC12F675(SN)@SOIC8 [CX1016]  
PIC12F675(SN)@SOIC8(ISP) [CX0001]  
PIC12F675@DFN8 [CX4005] PIC12F675@DFN8(ISP) [CX0001]  
PIC12F675@SSOP20 [CX1026] PIC12F675@SSOP20(ISP) [CX0001]  
PIC12F683 [CX0001] PIC12F683(4-WORD PRO) [CX0001]  
PIC12F683(ISP) [CX0001] PIC12F683(MD)@DFN8 [CX4004]  
PIC12F683(MD)@DFN8(4-WORD PRO) [CX4004]  
PIC12F683(MD)@DFN8(ISP) [CX0001] PIC12F683(MF)@DFN8 [CX4005]  
PIC12F683(MF)@DFN8(4-WORD PRO) [CX4005]  
PIC12F683(MF)@DFN8(ISP) [CX0001] PIC12F683(SM)@SOIC8 [CX1032]  
PIC12F683(SM)@SOIC8(4-WORD PRO) [CX1032]  
PIC12F683(SM)@SOIC8(ISP) [CX0001]  
PIC12F683(SN)@SOIC8 [CX1016]  
PIC12F683(SN)@SOIC8(4-WORD PRO) [CX1016]  
PIC12F683(SN)@SOIC8(ISP) [CX0001]  
PIC12F752 [CX0001] PIC12F752(ISP) [CX0001]  
PIC12F752@DFN8 [CX4003] PIC12F752@DFN8-S [CX4005]  
PIC12F752@MSOP8 [CX1015] PIC12F752@SOIC8 [CX1045]  
PIC12HV609 [CX0001] PIC12HV609(ISP) [CX0001]  
PIC12HV609@DFN8 [CX4003] PIC12HV609@DFN8(ISP) [CX0001]  
PIC12HV609@DFN8-S [CX4005] PIC12HV609@DFN8-S(ISP) [CX0001]  
PIC12HV609@MSOP8 [CX1015] PIC12HV609@MSOP8(ISP) [CX0001]  
PIC12HV609@SOIC8 [CX1045] PIC12HV609@SOIC8(ISP) [CX0001]  
PIC12HV615 [CX0001] PIC12HV615(ISP) [CX0001]  
PIC12HV615@DFN8 [CX4003] PIC12HV615@DFN8(ISP) [CX0001]  
PIC12HV615@DFN8-S [CX4005] PIC12HV615@DFN8-S(ISP) [CX0001]  
PIC12HV615@MSOP8 [CX1015] PIC12HV615@MSOP8(ISP) [CX0001]  
PIC12HV615@SOIC8 [CX1045] PIC12HV615@SOIC8(ISP) [CX0001]  
PIC12HV752 [CX0001] PIC12HV752(ISP) [CX0001]  
PIC12HV752@DFN8 [CX4003] PIC12HV752@DFN8-S [CX4005]  
PIC12HV752@MSOP8 [CX1015] PIC12HV752@SOIC8 [CX1045]  
PIC12LC508 [CX0001] PIC12LC508(ISP) [CX0001]  
PIC12LC508@SOIC8 [CX1032] PIC12LC508@SOIC8(ISP) [CX0001]  
PIC12LC508A [CX0001] PIC12LC508A(ISP) [CX0001]  
PIC12LC508A(SM)@SOIC8 [CX1032]  
PIC12LC508A(SM)@SOIC8(ISP) [CX0001]  
PIC12LC508A(SN)@SOIC8 [CX1016]  
PIC12LC508A(SN)@SOIC8(ISP) [CX0001]  
PIC12LC509 [CX0001] PIC12LC509(ISP) [CX0001]  
PIC12LC509(SM)@SOIC8 [CX1032]  
PIC12LC509(SM)@SOIC8(ISP) [CX0001]

PIC12LC509(SN)@SOIC8 [CX1016]  
PIC12LC509(SN)@SOIC8(ISP) [CX0001]  
PIC12LC509A [CX0001] PIC12LC509A(ISP) [CX0001]  
PIC12LC509A(SM)@SOIC8 [CX1032]  
PIC12LC509A(SM)@SOIC8(ISP) [CX0001]  
PIC12LC509A(SN)@SOIC8 [CX1016]  
PIC12LC509A(SN)@SOIC8(ISP) [CX0001]  
PIC12LC671 [CX0001] PIC12LC671(ISP) [CX0001]  
PIC12LC671@DFN8 [CX4005] PIC12LC671@DFN8(ISP) [CX0001]  
PIC12LC671@SOIC8 [CX1044] PIC12LC671@SOIC8(ISP) [CX0001]  
PIC12LC672 [CX0001] PIC12LC672(ISP) [CX0001]  
PIC12LC672@DFN8 [CX4005] PIC12LC672@DFN8(ISP) [CX0001]  
PIC12LC672@SOIC8 [CX1044] PIC12LC672@SOIC8(ISP) [CX0001]  
PIC12LF1501 [CX0001] PIC12LF1501(ISP) [CX0001]  
PIC12LF1501(MC)@DFN8 [CX4002] PIC12LF1501(MF)@DFN8 [CX4003]  
PIC12LF1501@DFN8(ISP) [CX0001] PIC12LF1501@MSOP8 [CX1015]  
PIC12LF1501@MSOP8(ISP) [CX0001] PIC12LF1501@SOIC8 [CX1045]  
PIC12LF1501@SOIC8(ISP) [CX0001] PIC12LF1822 [CX0001]  
PIC12LF1822(8-word) [CX0001] PIC12LF1822(ISP)(HV) [CX0001]  
PIC12LF1822(LV) [CX0001] PIC12LF1822(LVISP) [CX0001]  
PIC12LF1822@DFN8 [CX4003]  
PIC12LF1822@DFN8(8-word) [CX4003]  
PIC12LF1822@DFN8(ISP)(HV) [CX0001]  
PIC12LF1822@DFN8(LV) [CX4002] PIC12LF1822@SOIC8 [CX1045]  
PIC12LF1822@SOIC8(8-word) [CX1045]  
PIC12LF1822@SOIC8(ISP)(HV) [CX0001]  
PIC12LF1822@SOIC8(LV) [CX1045] PIC12LF1840 [CX0001]  
PIC12LF1840(ISP)(HV) [CX0001] PIC12LF1840@DFN8 [CX4003]  
PIC12LF1840@DFN8(ISP)(HV) [CX0001]  
PIC12LF1840@SOIC8 [CX1045]  
PIC12LF1840@SOIC8(ISP)(HV) [CX0001]  
PIC12LF1840E [CX0001] PIC12LF1840E@DFN8 [CX4003]  
PIC12LF1840E@SOIC8 [CX1045] PIC12LF1840T48A [CX1000]  
PIC12LF508 [CX0001] PIC12LF508(ISP) [CX0001]  
PIC12LF508@MSOP8 [CX1015] PIC12LF508@MSOP8(ISP) [CX0001]  
PIC12LF508@SOIC8 [CX1016] PIC12LF508@SOIC8(ISP) [CX0001]  
PIC12LF509 [CX0001] PIC12LF509(ISP) [CX0001]  
PIC12LF509@MSOP8 [CX1015] PIC12LF509@MSOP8(ISP) [CX0001]  
PIC12LF509@SOIC8 [CX1016] PIC12LF509@SOIC8(ISP) [CX0001]  
PIC12LF519 [CX0001] PIC12LF519(ISP) [CX0001]  
PIC12LF519@DFN8 [CX4002] PIC12LF519@DFN8(ISP) [CX0001]  
PIC12LF519@MSOP8 [CX1015] PIC12LF519@MSOP8(ISP) [CX0001]  
PIC12LF519@SOIC8 [CX1045] PIC12LF519@SOIC8(ISP) [CX0001]  
PIC14000 [CX0001] PIC14000(ISP) [CX0001]  
PIC14000@SOIC28 [CX1033] PIC14000@SOIC28(ISP) [CX0001]  
PIC14000@SSOP28 [CX1026] PIC14000@SSOP28(ISP) [CX0001]  
PIC16C432 [CX0001] PIC16C432(ISP) [CX0001]  
PIC16C432@SSOP20 [CX1026] PIC16C432@SSOP20(ISP) [CX0001]  
PIC16C433 [CX0001] PIC16C433(ISP) [CX0001]  
PIC16C433@SOIC18 PIC16C433@SOIC18(ISP) [CX0001]  
PIC16C505 [CX0001] PIC16C505@SOIC14 [CX1016]  
PIC16C52 [CX0001] PIC16C52@SOIC18 [CX1033]  
PIC16C54 [CX0001] PIC16C54@SOIC18 [CX1033]  
PIC16C54A [CX0001] PIC16C54A@SOIC18 [CX1033]  
PIC16C54A@SSOP20 [CX1026] PIC16C54B [CX0001]  
PIC16C54B@SOIC18 [CX1033] PIC16C54B@SSOP20 [CX1026]  
PIC16C54C [CX0001] PIC16C54C@SOIC18 [CX1033]  
PIC16C54C@SSOP20 [CX1026] PIC16C55 [CX0001]  
PIC16C55@SOIC28 [CX1033] PIC16C554 [CX0001]



PIC16C554(ISP) [CX0001]                    PIC16C554@SOIC18 [CX1033]  
PIC16C554@SOIC18(ISP) [CX0001]           PIC16C554@SSOP20 [CX1026]  
PIC16C554@SSOP20(ISP) [CX0001]           PIC16C556 [CX0001]  
PIC16C556(ISP) [CX0001]                    PIC16C556@SOIC18 [CX1033]  
PIC16C556@SOIC18(ISP) [CX0001]           PIC16C558 [CX0001]  
PIC16C558(ISP) [CX0001]                    PIC16C558@SOIC18 [CX1033]  
PIC16C558@SOIC18(ISP) [CX0001]           PIC16C558@SSOP20 [CX1026]  
PIC16C558@SSOP20(ISP) [CX0001]           PIC16C55A [CX0001]  
PIC16C55A@SOIC28 [CX1033]                  PIC16C55A@SSOP28 [CX1026]  
PIC16C56 [CX0001]                           PIC16C56@SOIC18 [CX1033]  
PIC16C56A [CX0001]                          PIC16C56A@SOIC18 [CX1033]  
PIC16C56A@SSOP20 [CX1026]                  PIC16C57 [CX0001]  
PIC16C57@SOIC28 [CX1033]                   PIC16C57@SSOP28 [CX1026]  
PIC16C57C [CX0001]                          PIC16C57C@SOIC28 [CX1033]  
PIC16C57C@SSOP28 [CX1026]                  PIC16C58 [CX0001]  
PIC16C58@SOIC18 [CX1033]                   PIC16C58A [CX0001]  
PIC16C58A@SOIC18 [CX1033]                  PIC16C58A@SSOP20 [CX1026]  
PIC16C58B [CX0001]                          PIC16C58B@SOIC18 [CX1033]  
PIC16C58B@SSOP20 [CX1026]                  PIC16C61 [CX0001]  
PIC16C61(ISP) [CX0001]                      PIC16C61@SOIC18 [CX1033]  
PIC16C61@SOIC18(ISP) [CX0001]              PIC16C62 [CX0001]  
PIC16C62(ISP) [CX0001]                      PIC16C62@SOIC28 [CX1033]  
PIC16C62@SOIC28(ISP) [CX0001]              PIC16C62@SSOP28 [CX1026]  
PIC16C62@SSOP28(ISP) [CX0001]              PIC16C620 [CX0001]  
PIC16C620(ISP) [CX0001]                      PIC16C620@SOIC18 [CX1033]  
PIC16C620@SOIC18(ISP) [CX0001]              PIC16C620A [CX0001]  
PIC16C620A(ISP) [CX0001]                    PIC16C620A@SOIC18 [CX1033]  
PIC16C620A@SOIC18(ISP) [CX0001]            PIC16C620A@SSOP20 [CX1026]  
PIC16C620A@SSOP20(ISP) [CX0001]           PIC16C621 [CX0001]  
PIC16C621(ISP) [CX0001]                      PIC16C621@SOIC18 [CX1033]  
PIC16C621@SOIC18(ISP) [CX0001]              PIC16C621A [CX0001]  
PIC16C621A(ISP) [CX0001]                    PIC16C621A@SOIC18 [CX1033]  
PIC16C621A@SOIC18(ISP) [CX0001]            PIC16C621A@SSOP20 [CX1026]  
PIC16C621A@SSOP20(ISP) [CX0001]           PIC16C622 [CX0001]  
PIC16C622(ISP) [CX0001]                      PIC16C622@SOIC18 [CX1033]  
PIC16C622@SOIC18(ISP) [CX0001]              PIC16C622A [CX0001]  
PIC16C622A(ISP) [CX0001]                    PIC16C622A@SOIC18 [CX1033]  
PIC16C622A@SOIC18(ISP) [CX0001]            PIC16C622A@SSOP20 [CX1026]  
PIC16C622A@SSOP20(ISP) [CX0001]           PIC16C625 [CX0001]  
PIC16C625(ISP) [CX0001]                      PIC16C625@SOIC18 [CX1033]  
PIC16C625@SOIC18(ISP) [CX0001]              PIC16C62A [CX0001]  
PIC16C62A(ISP) [CX0001]                      PIC16C62A@SOIC28 [CX1033]  
PIC16C62A@SOIC28(ISP) [CX0001]              PIC16C62A@SSOP28 [CX1026]  
PIC16C62A@SSOP28(ISP) [CX0001]              PIC16C62B [CX0001]  
PIC16C62B(ISP) [CX0001]                      PIC16C62B@SOIC28 [CX1033]  
PIC16C62B@SOIC28(ISP) [CX0001]              PIC16C62B@SSOP28 [CX1026]  
PIC16C62B@SSOP28(ISP) [CX0001]              PIC16C63 [CX0001]  
PIC16C63(ISP) [CX0001]                      PIC16C63@SOIC28 [CX1033]  
PIC16C63@SOIC28(ISP) [CX0001]              PIC16C63A [CX0001]  
PIC16C63A(ISP) [CX0001]                      PIC16C63A@SOIC28 [CX1033]  
PIC16C63A@SOIC28(ISP) [CX0001]              PIC16C63A@SSOP28 [CX1026]  
PIC16C63A@SSOP28(ISP) [CX0001]              PIC16C64 [CX0001]  
PIC16C64(ISP) [CX0001]                      PIC16C64@PLCC44 [CX2044]  
PIC16C64@PLCC44(ISP) [CX0001]              PIC16C64@TQFP44 [CX3003]  
PIC16C64@TQFP44(ISP) [CX0001]              PIC16C641 [CX0001]  
PIC16C641@SOIC28 [CX1033]                   PIC16C641@SSOP28 [CX1026]  
PIC16C642 [CX0001]                          PIC16C642@SOIC28 [CX1033]  
PIC16C642@SSOP28 [CX1026]                  PIC16C64A [CX0001]  
PIC16C64A(ISP) [CX0001]                    PIC16C64A@PLCC44 [CX2044]

PIC16C64A@PLCC44(ISP) [CX0001]  
PIC16C64A@TQFP44(ISP) [CX0001]  
PIC16C65(ISP) [CX0001]  
PIC16C65@PLCC44(ISP) [CX0001]  
PIC16C65@TQFP44(ISP) [CX0001]  
PIC16C65A(ISP) [CX0001]  
PIC16C65A@PLCC44(ISP) [CX0001]  
PIC16C65A@TQFP44(ISP) [CX0001]  
PIC16C65B(ISP) [CX0001]  
PIC16C65B@PLCC44(ISP) [CX0001]  
PIC16C65B@TQFP44(ISP) [CX0001]  
PIC16C66(ISP) [CX0001]  
PIC16C66@SOIC28(ISP) [CX0001]  
PIC16C661@PLCC44 [CX2044]  
PIC16C662 [CX0001]  
PIC16C662@TQFP44 [CX3003]  
PIC16C67(ISP) [CX0001]  
PIC16C67@PLCC44(ISP) [CX0001]  
PIC16C67@TQFP44(ISP) [CX0001]  
PIC16C70(ISP) [CX0001]  
PIC16C70@SOIC18(ISP) [CX0001]  
PIC16C71(ISP) [CX0001]  
PIC16C71@SOIC18(ISP) [CX0001]  
PIC16C710(ISP) [CX0001]  
PIC16C710@SOIC18(ISP) [CX0001]  
PIC16C710@SSOP20(ISP) [CX0001]  
PIC16C711(ISP) [CX0001]  
PIC16C711@SOIC18(ISP) [CX0001]  
PIC16C711@SSOP20(ISP) [CX0001]  
PIC16C712(ISP) [CX0001]  
PIC16C712@SOIC18(ISP) [CX0001]  
PIC16C712@SSOP20(ISP) [CX0001]  
PIC16C715@SOIC18 [CX1033]  
PIC16C716 [CX0001]  
PIC16C716@SOIC18 [CX1033]  
PIC16C716@SSOP20 [CX1026]  
PIC16C717 [CX0001]  
PIC16C717@SOIC18  
PIC16C717@SSOP20 [CX1026]  
PIC16C71A [CX0001]  
PIC16C71A@SOIC18 [CX1033]  
PIC16C72 [CX0001]  
PIC16C72@SOIC28 [CX1033]  
PIC16C72@SSOP28 [CX1026]  
PIC16C72A [CX0001]  
PIC16C72A@SOIC28 [CX1033]  
PIC16C72A@SSOP28 [CX1026]  
PIC16C73 [CX0001]  
PIC16C73@SOIC28 [CX1033]  
PIC16C73A [CX0001]  
PIC16C73A@SOIC28 [CX1033]  
PIC16C73B [CX0001]  
PIC16C73B@SOIC28 [CX1033]  
PIC16C73B@SSOP28 [CX1026]  
PIC16C74 [CX0001]  
PIC16C74@PLCC44 [CX2044]  
PIC16C74@TQFP44 [CX3003]  
PIC16C745 [CX0001]  
PIC16C745@SOIC28

PIC16C64A@TQFP44 [CX3003]  
PIC16C65 [CX0001]  
PIC16C65@PLCC44 [CX2044]  
PIC16C65@TQFP44 [CX3003]  
PIC16C65A [CX0001]  
PIC16C65A@PLCC44 [CX2044]  
PIC16C65A@TQFP44 [CX3003]  
PIC16C65B [CX0001]  
PIC16C65B@PLCC44 [CX2044]  
PIC16C65B@TQFP44 [CX3003]  
PIC16C66 [CX0001]  
PIC16C66@SOIC28 [CX1033]  
PIC16C661 [CX0001]  
PIC16C661@TQFP44 [CX3003]  
PIC16C662@PLCC44 [CX2044]  
PIC16C67 [CX0001]  
PIC16C67@PLCC44 [CX2044]  
PIC16C67@TQFP44 [CX3003]  
PIC16C70 [CX0001]  
PIC16C70@SOIC18 [CX1033]  
PIC16C71 [CX0001]  
PIC16C71@SOIC18 [CX1033]  
PIC16C710 [CX0001]  
PIC16C710@SOIC18 [CX1033]  
PIC16C710@SSOP20 [CX1026]  
PIC16C711 [CX0001]  
PIC16C711@SOIC18 [CX1033]  
PIC16C711@SSOP20 [CX1026]  
PIC16C712 [CX0001]  
PIC16C712@SOIC18 [CX1033]  
PIC16C712@SSOP20 [CX1026]  
PIC16C715 [CX0001]  
PIC16C715@SSOP20 [CX1026]  
PIC16C716(ISP) [CX0001]  
PIC16C716@SOIC18(ISP) [CX0001]  
PIC16C716@SSOP20(ISP) [CX0001]  
PIC16C717(ISP) [CX0001]  
PIC16C717@SOIC18(ISP) [CX0001]  
PIC16C717@SSOP20(ISP) [CX0001]  
PIC16C71A(ISP) [CX0001]  
PIC16C71A@SOIC18(ISP) [CX0001]  
PIC16C72(ISP) [CX0001]  
PIC16C72@SOIC28(ISP) [CX0001]  
PIC16C72@SSOP28(ISP) [CX0001]  
PIC16C72A(ISP) [CX0001]  
PIC16C72A@SOIC28(ISP) [CX0001]  
PIC16C72A@SSOP28(ISP) [CX0001]  
PIC16C73(ISP) [CX0001]  
PIC16C73@SOIC28(ISP) [CX0001]  
PIC16C73A(ISP) [CX0001]  
PIC16C73A@SOIC28(ISP) [CX0001]  
PIC16C73B(ISP) [CX0001]  
PIC16C73B@SOIC28(ISP) [CX0001]  
PIC16C73B@SSOP28(ISP) [CX0001]  
PIC16C74(ISP) [CX0001]  
PIC16C74@PLCC44(ISP) [CX0001]  
PIC16C74@TQFP44(ISP) [CX0001]  
PIC16C745(ISP) [CX0001]  
PIC16C745@SOIC28(ISP) [CX0001]

PIC16C74A [CX0001]  
PIC16C74A@PLCC44 [CX2044]  
PIC16C74A@TQFP44 [CX3003]  
PIC16C74B [CX0001]  
PIC16C74B@MQFP44 [CX3002]  
PIC16C74B@PLCC44 [CX2044]  
PIC16C74B@TQFP44 [CX3003]  
PIC16C76 [CX0001]  
PIC16C76@SOIC28 [CX1033]  
PIC16C765 [CX0001]  
PIC16C765@PLCC44 [CX2044]  
PIC16C765@TQFP44 [CX3003]  
PIC16C77 [CX0001]  
PIC16C77@PLCC44 [CX2044]  
PIC16C77@TQFP44 [CX3003]  
PIC16C770 [CX0001]  
PIC16C770@SOIC20  
PIC16C770@SSOP20 [CX1026]  
PIC16C771 [CX0001]  
PIC16C771@SOIC20  
PIC16C771@SSOP20 [CX1026]  
PIC16C773 [CX0001]  
PIC16C773@SOIC28  
PIC16C773@SSOP28 [CX1026]  
PIC16C774 [CX0001]  
PIC16C774@PLCC44 [CX2044]  
PIC16C774@TQFP44 [CX3003]  
PIC16C781 [CX0001]  
PIC16C781@SOIC20  
PIC16C781@SSOP20 [CX1026]  
PIC16C782 [CX0001]  
PIC16C782@SOIC20  
PIC16C782@SSOP20 [CX1026]  
PIC16C84 [CX0001]  
PIC16C84@SOIC18 [CX1033]  
PIC16C923@PLCC68 [CX2068]  
PIC16C923@SDIP64 [CX0064]  
PIC16C923@TQFP64 [CX3011]  
PIC16C924@PLCC68 [CX2068]  
PIC16C924@SDIP64 [CX0064]  
PIC16C924@TQFP64 [CX3011]  
PIC16C925@PLCC68 [CX2068]  
PIC16C925@TQFP64 [CX3011]  
PIC16C926@PLCC68 [CX2068]  
PIC16C926@TQFP64 [CX3011]  
PIC16CE623 [CX0001]  
PIC16CE623@SOIC18 [CX1033]  
PIC16CE624 [CX0001]  
PIC16CE624@SOIC18 [CX1033]  
PIC16CE625 [CX0001]  
PIC16CE625@SOIC18 [CX1033]  
PIC16CE625@SSOP20 [CX1026]  
PIC16CR83 [CX0001]  
PIC16CR83@SOIC18 [CX1033]  
PIC16CR84 [CX0001]  
PIC16CR84@SOIC18 [CX1033]  
PIC16F1454 [CX0001]  
PIC16F1454@QFN16 [CX4010]  
PIC16F1454@TSSOP14 [CX1000]

PIC16C74A(ISP) [CX0001]  
PIC16C74A@PLCC44(ISP) [CX0001]  
PIC16C74A@TQFP44(ISP) [CX0001]  
PIC16C74B(ISP) [CX0001]  
PIC16C74B@MQFP44(ISP) [CX0001]  
PIC16C74B@PLCC44(ISP) [CX0001]  
PIC16C74B@TQFP44(ISP) [CX0001]  
PIC16C76(ISP) [CX0001]  
PIC16C76@SOIC28(ISP) [CX0001]  
PIC16C765(ISP) [CX0001]  
PIC16C765@PLCC44(ISP) [CX0001]  
PIC16C765@TQFP44(ISP) [CX0001]  
PIC16C77(ISP) [CX0001]  
PIC16C77@PLCC44(ISP) [CX0001]  
PIC16C77@TQFP44(ISP) [CX0001]  
PIC16C770(ISP) [CX0001]  
PIC16C770@SOIC20(ISP) [CX0001]  
PIC16C770@SSOP20(ISP) [CX0001]  
PIC16C771(ISP) [CX0001]  
PIC16C771@SOIC20(ISP) [CX0001]  
PIC16C771@SSOP20(ISP) [CX0001]  
PIC16C773(ISP) [CX0001]  
PIC16C773@SOIC28(ISP) [CX0001]  
PIC16C773@SSOP28(ISP) [CX0001]  
PIC16C774(ISP) [CX0001]  
PIC16C774@PLCC44(ISP) [CX0001]  
PIC16C774@TQFP44(ISP) [CX0001]  
PIC16C781(ISP) [CX0001]  
PIC16C781@SOIC20(ISP) [CX0001]  
PIC16C781@SSOP20(ISP) [CX0001]  
PIC16C782(ISP) [CX0001]  
PIC16C782@SOIC20(ISP) [CX0001]  
PIC16C782@SSOP20(ISP) [CX0001]  
PIC16C84(ISP) [CX0001]  
PIC16C84@SOIC18(ISP) [CX0001]  
PIC16C923@PLCC68(ISP) [CX0001]  
PIC16C923@SDIP64(ISP) [CX0001]  
PIC16C923@TQFP64(ISP) [CX0001]  
PIC16C924@PLCC68(ISP) [CX0001]  
PIC16C924@SDIP64(ISP) [CX0001]  
PIC16C924@TQFP64(ISP) [CX0001]  
PIC16C925@PLCC68(ISP) [CX0001]  
PIC16C925@TQFP64(ISP) [CX0001]  
PIC16C926@PLCC68(ISP) [CX0001]  
PIC16C926@TQFP64(ISP) [CX0001]  
PIC16CE623(ISP) [CX0001]  
PIC16CE623@SOIC18(ISP) [CX0001]  
PIC16CE624(ISP) [CX0001]  
PIC16CE624@SOIC18(ISP) [CX0001]  
PIC16CE625(ISP) [CX0001]  
PIC16CE625@SOIC18(ISP) [CX0001]  
PIC16CE625@SSOP20(ISP) [CX0001]  
PIC16CR83(ISP) [CX0001]  
PIC16CR83@SOIC18(ISP) [CX0001]  
PIC16CR84(ISP) [CX0001]  
PIC16CR84@SOIC18(ISP) [CX0001]  
PIC16F1454(ISP) [CX0001]  
PIC16F1454@SOIC14 [CX1016]  
PIC16F1455 [CX0001]

PIC16F1455(ISP) [CX0001]  
PIC16F1455@SOIC14 [CX1016]  
PIC16F1458 [CX0001]  
PIC16F1458@QFN20 [CX4011]  
PIC16F1458@SSOP20 [CX1026]  
PIC16F1459(ISP) [CX0001]  
PIC16F1459@SOIC20 [CX1033]  
PIC16F1503 [CX0001]  
PIC16F1503@QFN16 [CX4053]  
PIC16F1503@SOIC14 [CX1016]  
PIC16F1503@TSOP14 [CX1000]  
PIC16F1507 [CX0001]  
PIC16F1507@QFN20 [CX4011]  
PIC16F1507@SOIC20 [CX1033]  
PIC16F1507@SSOP20 [CX1026]  
PIC16F1508 [CX0001]  
PIC16F1508@QFN20 [CX4011]  
PIC16F1508@SOIC20 [CX1033]  
PIC16F1508@SSOP20 [CX1026]  
PIC16F1509 [CX0001]  
PIC16F1509@QFN20 [CX4011]  
PIC16F1509@SOIC20 [CX1033]  
PIC16F1509@SSOP20 [CX1026]  
PIC16F1512 [CX0001]  
PIC16F1512@SOIC18(ISP) [CX0001]  
PIC16F1512@SSOP28 [CX1026]  
PIC16F1512@UQFN28 [CX4036]  
PIC16F1513 [CX0001]  
PIC16F1513@SOIC18(ISP) [CX0001]  
PIC16F1513@SSOP28 [CX1026]  
PIC16F1513@UQFN28 [CX4036]  
PIC16F1516 [CX0001]  
PIC16F1516@SOIC18(ISP) [CX0001]  
PIC16F1516@SSOP28 [CX1026]  
PIC16F1516@UQFN28 [CX4036]  
PIC16F1517 [CX0001]  
PIC16F1517@TQFP44 [CX3003]  
PIC16F1517@UQFN40 [CX4039]  
PIC16F1518 [CX0001]  
PIC16F1518@SOIC18(ISP) [CX0001]  
PIC16F1518@SSOP28 [CX1026]  
PIC16F1518@UQFN28 [CX4036]  
PIC16F1519 [CX0001]  
PIC16F1519@TQFP44 [CX3003]  
PIC16F1519@UQFN40 [CX4039]  
PIC16F1526@QFN64 [CX3011]  
PIC16F1526@TQFP64 [CX3011]  
PIC16F1527@QFN64 [CX3011]  
PIC16F1527@TQFP64 [CX3011]  
PIC16F1782 [CX0001]  
PIC16F1782@SOIC28 [CX1033]  
PIC16F1782@SSOP28 [CX1026]  
PIC16F1782@UQFN28 [CX4014]  
PIC16F1783 [CX0001]  
PIC16F1783@SOIC28 [CX1033]  
PIC16F1783@SSOP28 [CX1026]  
PIC16F1783@UQFN28 [CX4014]  
PIC16F1784 [CX0001]  
PIC16F1784@QFN44 [CX4019]  
PIC16F1455@QFN16 [CX4010]  
PIC16F1455@TSSOP14 [CX1000]  
PIC16F1458(ISP) [CX0001]  
PIC16F1458@SOIC20 [CX1033]  
PIC16F1459 [CX0001]  
PIC16F1459@QFN20 [CX4011]  
PIC16F1459@SSOP20 [CX1026]  
PIC16F1503(ISP) [CX0001]  
PIC16F1503@QFN16(ISP) [CX0001]  
PIC16F1503@SOIC14(ISP) [CX0001]  
PIC16F1503@TSSOP14(ISP) [CX0001]  
PIC16F1507(ISP) [CX0001]  
PIC16F1507@QFN20(ISP) [CX0001]  
PIC16F1507@SOIC20(ISP) [CX0001]  
PIC16F1507@SSOP20(ISP) [CX0001]  
PIC16F1508(ISP) [CX0001]  
PIC16F1508@QFN20(ISP) [CX0001]  
PIC16F1508@SOIC20(ISP) [CX0001]  
PIC16F1508@SSOP20(ISP) [CX0001]  
PIC16F1509(ISP) [CX0001]  
PIC16F1509@QFN20(ISP) [CX0001]  
PIC16F1509@SOIC20(ISP) [CX0001]  
PIC16F1509@SSOP20(ISP) [CX0001]  
PIC16F1512(ISP) [CX0001]  
PIC16F1512@SOIC28 [CX1033]  
PIC16F1512@SSOP28(ISP) [CX0001]  
PIC16F1512@UQFN28(ISP) [CX0001]  
PIC16F1513(ISP) [CX0001]  
PIC16F1513@SOIC28 [CX1033]  
PIC16F1513@SSOP28(ISP) [CX0001]  
PIC16F1513@UQFN28(ISP) [CX0001]  
PIC16F1516(ISP) [CX0001]  
PIC16F1516@SOIC28 [CX1033]  
PIC16F1516@SSOP28(ISP) [CX0001]  
PIC16F1516@UQFN28(ISP) [CX0001]  
PIC16F1517(ISP) [CX0001]  
PIC16F1517@TQFP44(ISP) [CX0001]  
PIC16F1517@UQFN40(ISP) [CX0001]  
PIC16F1518(ISP) [CX0001]  
PIC16F1518@SOIC28 [CX1033]  
PIC16F1518@SSOP28(ISP) [CX0001]  
PIC16F1518@UQFN28(ISP) [CX0001]  
PIC16F1519(ISP) [CX0001]  
PIC16F1519@TQFP44(ISP) [CX0001]  
PIC16F1519@UQFN40(ISP) [CX0001]  
PIC16F1526@QFN64(ISP) [CX0001]  
PIC16F1526@TQFP64(ISP) [CX0001]  
PIC16F1527@QFN64(ISP) [CX0001]  
PIC16F1527@TQFP64(ISP) [CX0001]  
PIC16F1782(ISP) [CX0001]  
PIC16F1782@SOIC28(ISP) [CX0001]  
PIC16F1782@SSOP28(ISP) [CX0001]  
PIC16F1782@UQFN28(ISP) [CX0001]  
PIC16F1783(ISP) [CX0001]  
PIC16F1783@SOIC28(ISP) [CX0001]  
PIC16F1783@SSOP28(ISP) [CX0001]  
PIC16F1783@UQFN28(ISP) [CX0001]  
PIC16F1784(ISP) [CX0001]  
PIC16F1784@TQFP44 [CX3003]

PIC16F1784@UQFN40  
PIC16F1786(ISP) [CX0001]  
PIC16F1786@SOIC28 [CX1033]  
PIC16F1787 [CX0001]  
PIC16F1787@QFN44 [CX4019]  
PIC16F1787@UQFN40  
PIC16F1788(ISP) [CX0001]  
PIC16F1788@SOIC28 [CX1033]  
PIC16F1789 [CX0001]  
PIC16F1789@QFN44 [CX4019]  
PIC16F1789@UQFN40  
PIC16F1823(8-word) [CX0001]  
PIC16F1823(LV) [CX0001]  
PIC16F1823@QFN16(3\*3) [CX4008]  
PIC16F1823@QFN16(3\*3)(8-word) [CX4008]  
PIC16F1823@QFN16(3\*3)(ISP)(HV) [CX0001]  
PIC16F1823@QFN16(3\*3)(LV) [CX4008]  
PIC16F1823@QFN16(4\*4) [CX4010]  
PIC16F1823@QFN16(4\*4)(8-word) [CX4010]  
PIC16F1823@QFN16(4\*4)(ISP)(HV) [CX0001]  
PIC16F1823@QFN16(4\*4)(LV) [CX4010]  
PIC16F1823@SOIC14 [CX1016]  
PIC16F1823@SOIC14(8-word) [CX1016]  
PIC16F1823@SOIC14(ISP)(HV) [CX0001]  
PIC16F1823@SOIC14(LV) [CX1016] PIC16F1823@TSSOP14 [CX1000]  
PIC16F1823@TSSOP14(8-word) [CX1000]  
PIC16F1823@TSSOP14(ISP)(HV) [CX0001]  
PIC16F1823@TSSOP14(LV) [CX1000] PIC16F1824 [CX0001]  
PIC16F1824(8-word) [CX0001] PIC16F1824(ISP)(HV) [CX0001]  
PIC16F1824(LV) [CX0001] PIC16F1824(LVISP) [CX0001]  
PIC16F1824@QFN16(3\*3) [CX4008]  
PIC16F1824@QFN16(3\*3)(8-word) [CX4008]  
PIC16F1824@QFN16(3\*3)(ISP)(HV) [CX0001]  
PIC16F1824@QFN16(3\*3)(LV) [CX4008]  
PIC16F1824@QFN16(4\*4) [CX4010]  
PIC16F1824@QFN16(4\*4)(8-word) [CX4010]  
PIC16F1824@QFN16(4\*4)(ISP)(HV) [CX0001]  
PIC16F1824@QFN16(4\*4)(LV) [CX4010]  
PIC16F1824@SOIC14 [CX1016]  
PIC16F1824@SOIC14(8-word) [CX1016]  
PIC16F1824@SOIC14(ISP)(HV) [CX0001]  
PIC16F1824@SOIC14(LV) [CX1016] PIC16F1824@TSSOP14 [CX1000]  
PIC16F1824@TSSOP14(8-word) [CX1000]  
PIC16F1824@TSSOP14(ISP)(HV) [CX0001]  
PIC16F1824@TSSOP14(LV) [CX1000] PIC16F1825 [CX0001]  
PIC16F1825(8-word) [CX0001] PIC16F1825(ISP)(HV) [CX0001]  
PIC16F1825(LV) [CX0001] PIC16F1825(LVISP) [CX0001]  
PIC16F1825@QFN16(3\*3) [CX4008]  
PIC16F1825@QFN16(3\*3)(8-word) [CX4008]  
PIC16F1825@QFN16(3\*3)(ISP)(HV) [CX0001]  
PIC16F1825@QFN16(3\*3)(LV) [CX4008]  
PIC16F1825@QFN16(4\*4) [CX4010]  
PIC16F1825@QFN16(4\*4)(8-word) [CX4010]  
PIC16F1825@QFN16(4\*4)(ISP)(HV) [CX0001]  
PIC16F1825@QFN16(4\*4)(LV) [CX4010]  
PIC16F1825@SOIC14 [CX1016]  
PIC16F1825@SOIC14(8-word) [CX1016]  
PIC16F1825@SOIC14(ISP)(HV) [CX0001]  
PIC16F1825@SOIC14(LV) [CX1016] PIC16F1825@TSSOP14 [CX1000]

PIC16F1825@TSSOP14(8-word) [CX1000]  
PIC16F1825@TSSOP14(ISP)(HV) [CX0001]  
PIC16F1825@TSSOP14(LV) [CX1000] PIC16F1826 [CX0001]  
PIC16F1826(8-word) [CX0001] PIC16F1826(ISP)(HV) [CX0001]  
PIC16F1826(LV) [CX0001] PIC16F1826(LVISP) [CX0001]  
PIC16F1826@QFN28 [CX4014]  
PIC16F1826@QFN28(8-word) [CX4014]  
PIC16F1826@QFN28(ISP)(HV) [CX0001]  
PIC16F1826@QFN28(LV) [CX4014] PIC16F1826@SOIC18 [CX1033]  
PIC16F1826@SOIC18(8-word) [CX1033]  
PIC16F1826@SOIC18(ISP)(HV) [CX0001]  
PIC16F1826@SOIC18(LV) [CX1033] PIC16F1826@SSOP20 [CX1070]  
PIC16F1826@SSOP20(8-word) [CX1070]  
PIC16F1826@SSOP20(ISP)(HV) [CX0001]  
PIC16F1826@SSOP20(LV) [CX1026] PIC16F1827 [CX0001]  
PIC16F1827(8-word) [CX0001] PIC16F1827(ISP)(HV) [CX0001]  
PIC16F1827(LV) [CX0001] PIC16F1827(LVISP) [CX0001]  
PIC16F1827@QFN28 [CX4014]  
PIC16F1827@QFN28(8-word) [CX4014]  
PIC16F1827@QFN28(ISP)(HV) [CX0001]  
PIC16F1827@QFN28(LV) [CX4014] PIC16F1827@SOIC18 [CX1033]  
PIC16F1827@SOIC18(8-word) [CX1033]  
PIC16F1827@SOIC18(ISP)(HV) [CX0001]  
PIC16F1827@SOIC18(LV) [CX1033] PIC16F1827@SSOP20 [CX1070]  
PIC16F1827@SSOP20(8-word) [CX1070]  
PIC16F1827@SSOP20(ISP)(HV) [CX0001]  
PIC16F1827@SSOP20(LV) [CX1026] PIC16F1828 [CX0001]  
PIC16F1828(8-word) [CX0001] PIC16F1828(ISP)(HV) [CX0001]  
PIC16F1828(LV) [CX0001] PIC16F1828(LVISP) [CX0001]  
PIC16F1828@QFN20 [CX4011]  
PIC16F1828@QFN20(8-word) [CX4011]  
PIC16F1828@QFN20(ISP)(HV) [CX0001]  
PIC16F1828@QFN20(LV) [CX4011] PIC16F1828@SOIC20 [CX1033]  
PIC16F1828@SOIC20(8-word) [CX1033]  
PIC16F1828@SOIC20(ISP)(HV) [CX0001]  
PIC16F1828@SOIC20(LV) [CX1033] PIC16F1828@TSSOP20 [CX1070]  
PIC16F1828@TSSOP20(8-word) [CX1070]  
PIC16F1828@TSSOP20(ISP)(HV) [CX0001]  
PIC16F1828@TSSOP20(LV) [CX1026] PIC16F1829 [CX0001]  
PIC16F1829(8-word) [CX0001] PIC16F1829(ISP)(HV) [CX0001]  
PIC16F1829(LV) [CX0001] PIC16F1829(LVISP) [CX0001]  
PIC16F1829@QFN20 [CX4011]  
PIC16F1829@QFN20(8-word) [CX4011]  
PIC16F1829@QFN20(ISP)(HV) [CX0001]  
PIC16F1829@QFN20(LV) [CX4011] PIC16F1829@SOIC20 [CX1033]  
PIC16F1829@SOIC20(8-word) [CX1033]  
PIC16F1829@SOIC20(ISP)(HV) [CX0001]  
PIC16F1829@SOIC20(LV) [CX1033] PIC16F1829@TSSOP20 [CX1070]  
PIC16F1829@TSSOP20(8-word) [CX1070]  
PIC16F1829@TSSOP20(ISP)(HV) [CX0001]  
PIC16F1829@TSSOP20(LV) [CX1026] PIC16F1847 [CX0001]  
PIC16F1847(ISP)(HV) [CX0001] PIC16F1847@QFN28 [CX4014]  
PIC16F1847@QFN28(ISP)(HV) [CX0001]  
PIC16F1847@SOIC18 [CX1033]  
PIC16F1847@SOIC18(ISP)(HV) [CX0001]  
PIC16F1847@SSOP20 [CX1026]  
PIC16F1847@SSOP20(ISP)(HV) [CX0001]  
PIC16F1847E [CX0001] PIC16F1847E@QFN28 [CX4014]  
PIC16F1847E@SOIC18 [CX1033] PIC16F1847E@SSOP20 [CX1026]

PIC16F1933 [CX0001] PIC16F1933(ISP)(HV) [CX0001]  
PIC16F1933@QFN28 [CX4014]  
PIC16F1933@QFN28(ISP)(HV) [CX0001]  
PIC16F1933@QFN28[8-word pro] [CX4014]  
PIC16F1933@SOIC28 [CX1033]  
PIC16F1933@SOIC28(ISP)(HV) [CX0001]  
PIC16F1933@SOIC28[8-word pro] [CX1033]  
PIC16F1933@SSOP28 [CX1026]  
PIC16F1933@SSOP28(ISP)(HV) [CX0001]  
PIC16F1933@SSOP28[8-word pro] [CX1026]  
PIC16F1933@UQFN28 [CX4036] PIC16F1933[8-word pro] [CX0001]  
PIC16F1934 [CX0001] PIC16F1934(ISP)(HV) [CX0001]  
PIC16F1934@QFN44 [CX4019]  
PIC16F1934@QFN44(ISP)(HV) [CX0001]  
PIC16F1934@QFN44[8-word pro] [CX4019]  
PIC16F1934@TQFP44 [CX3003]  
PIC16F1934@TQFP44(ISP)(HV) [CX0001]  
PIC16F1934@TQFP44[8-word pro] [CX3003]  
PIC16F1934[8-word pro] [CX0001] PIC16F1936 [CX0001]  
PIC16F1936(ISP)(HV) [CX0001] PIC16F1936@QFN28 [CX4014]  
PIC16F1936@QFN28(ISP)(HV) [CX0001]  
PIC16F1936@QFN28[8-word pro] [CX4014]  
PIC16F1936@SOIC28 [CX1033]  
PIC16F1936@SOIC28(ISP)(HV) [CX0001]  
PIC16F1936@SOIC28[8-word pro] [CX1033]  
PIC16F1936@SSOP28 [CX1026]  
PIC16F1936@SSOP28(ISP)(HV) [CX0001]  
PIC16F1936@SSOP28[8-word pro] [CX1026]  
PIC16F1936@UQFN28 [CX4036] PIC16F1936[8-word pro] [CX0001]  
PIC16F1937 [CX0001] PIC16F1937(ISP)(HV) [CX0001]  
PIC16F1937@QFN44 [CX4019]  
PIC16F1937@QFN44(ISP)(HV) [CX0001]  
PIC16F1937@QFN44[8-word pro] [CX4019]  
PIC16F1937@TQFP44 [CX3003]  
PIC16F1937@TQFP44(ISP)(HV) [CX0001]  
PIC16F1937@TQFP44[8-word pro] [CX3003]  
PIC16F1937[8-word pro] [CX0001] PIC16F1938 [CX0001]  
PIC16F1938(ISP)(HV) [CX0001] PIC16F1938@QFN28 [CX4014]  
PIC16F1938@QFN28(ISP)(HV) [CX0001]  
PIC16F1938@QFN28[8-word pro] [CX4014]  
PIC16F1938@SOIC28 [CX1033]  
PIC16F1938@SOIC28(ISP)(HV) [CX0001]  
PIC16F1938@SOIC28[8-word pro] [CX1033]  
PIC16F1938@SSOP28 [CX1026]  
PIC16F1938@SSOP28(ISP)(HV) [CX0001]  
PIC16F1938@SSOP28[8-word pro] [CX1026]  
PIC16F1938@UQFN28 [CX4036] PIC16F1938[8-word pro] [CX0001]  
PIC16F1939 [CX0001] PIC16F1939(ISP)(HV) [CX0001]  
PIC16F1939@QFN44 [CX4019]  
PIC16F1939@QFN44(ISP)(HV) [CX0001]  
PIC16F1939@QFN44[8-word pro] [CX4019]  
PIC16F1939@TQFP44 [CX3003]  
PIC16F1939@TQFP44(ISP)(HV) [CX0001]  
PIC16F1939@TQFP44[8-word pro] [CX3003]  
PIC16F1939[8-word pro] [CX0001] PIC16F1946@QFN64 [CX4023]  
PIC16F1946@QFN64(ISP)(HV) [CX0001]  
PIC16F1946@QFN64[8-word pro] [CX4023]  
PIC16F1946@TQFP64 [CX3011]  
PIC16F1946@TQFP64(ISP)(HV) [CX0001]

PIC16F1946@TQFP64[8-word pro] [CX3011]  
PIC16F1947@QFN64 [CX4023]  
PIC16F1947@QFN64(ISP)(HV) [CX0001]  
PIC16F1947@QFN64[8-word pro] [CX4023]  
PIC16F1947@TQFP64 [CX3011]  
PIC16F1947@TQFP64(ISP)(HV) [CX0001]  
PIC16F1947@TQFP64[8-word pro] [CX3011]  
PIC16F505 [CX0001] PIC16F505(ISP) [CX0001]  
PIC16F505@SOIC14 [CX1065] PIC16F505@SOIC14(ISP) [CX0001]  
PIC16F505@TSSOP14 [CX1000] PIC16F505@TSSOP14(ISP) [CX0001]  
PIC16F506 [CX0001] PIC16F506(ISP) [CX0001]  
PIC16F506@SOIC14 [CX1030] PIC16F506@SOIC14(ISP) [CX0001]  
PIC16F506@TSSOP14 [CX1001] PIC16F506@TSSOP14(ISP) [CX0001]  
PIC16F526 [CX0001] PIC16F526(ISP) [CX0001]  
PIC16F526@SOIC14 [CX1016] PIC16F526@SOIC14(ISP) [CX0001]  
PIC16F526@TSSOP14 [CX1000] PIC16F526@TSSOP14(ISP) [CX0001]  
PIC16F527 [CX0001] PIC16F527(ISP) [CX0001]  
PIC16F527@QFN20 [CX1016] PIC16F527@SOIC20 [CX1033]  
PIC16F527@SSOP20 [CX1026] PIC16F54 [CX0001]  
PIC16F54(ISP) [CX0001] PIC16F54@SOIC18 [CX1033]  
PIC16F54@SOIC18(ISP) [CX0001] PIC16F54@SSOP20 [CX1026]  
PIC16F54@SSOP20(ISP) [CX0001] PIC16F57 [CX0001]  
PIC16F57(ISP) [CX0001] PIC16F57@SOIC28 [CX1033]  
PIC16F57@SOIC28(ISP) [CX0001] PIC16F57@SSOP28 [CX1026]  
PIC16F57@SSOP28(ISP) [CX0001] PIC16F59 [CX0001]  
PIC16F59(ISP) [CX0001] PIC16F59@PLCC44 [CX2044]  
PIC16F59@PLCC44(ISP) [CX0001] PIC16F59@TQFP44 [CX3003]  
PIC16F59@TQFP44(ISP) [CX0001] PIC16F610 [CX0001]  
PIC16F610(ISP) [CX0001] PIC16F610@QFN16 [CX4010]  
PIC16F610@QFN16(ISP) [CX0001] PIC16F610@SOIC14 [CX1016]  
PIC16F610@SOIC14(ISP) [CX0001] PIC16F610@TSSOP14 [CX1000]  
PIC16F610@TSSOP14(ISP) [CX0001] PIC16F616 [CX0001]  
PIC16F616(ISP) [CX0001] PIC16F616@QFN16 [CX4010]  
PIC16F616@QFN16(ISP) [CX0001] PIC16F616@SOIC14 [CX1016]  
PIC16F616@SOIC14(ISP) [CX0001] PIC16F616@TSSOP14 [CX1000]  
PIC16F616@TSSOP14(ISP) [CX0001] PIC16F627 [CX0001]  
PIC16F627(ISP) [CX0001] PIC16F627@SOIC18 [CX1033]  
PIC16F627@SOIC18(ISP) [CX0001] PIC16F627@SSOP20 [CX1026]  
PIC16F627@SSOP20(ISP) [CX0001] PIC16F627A [CX0001]  
PIC16F627A(ISP) [CX0001] PIC16F627A@SOIC18 [CX1033]  
PIC16F627A@SOIC18(ISP) [CX0001] PIC16F627A@SSOP20 [CX1026]  
PIC16F627A@SSOP20(ISP) [CX0001] PIC16F628 [CX0001]  
PIC16F628(ISP) [CX0001] PIC16F628@SOIC18 [CX1033]  
PIC16F628@SOIC18(ISP) [CX0001] PIC16F628@SSOP20 [CX1026]  
PIC16F628@SSOP20(ISP) [CX0001] PIC16F628A [CX0001]  
PIC16F628A(ISP) [CX0001] PIC16F628A@SOIC18 [CX1033]  
PIC16F628A@SOIC18(ISP) [CX0001] PIC16F628A@SSOP20 [CX1026]  
PIC16F628A@SSOP20(ISP) [CX0001] PIC16F630 [CX0001]  
PIC16F630(ISP) [CX0001] PIC16F630@SOIC14 [CX1065]  
PIC16F630@SOIC14(ISP) [CX0001] PIC16F630@TSSOP14 [CX1000]  
PIC16F630@TSSOP14(ISP) [CX0001] PIC16F631 [CX0001]  
PIC16F631(ISP) [CX0001] PIC16F631@QFN20 [CX4011]  
PIC16F631@QFN20(ISP) [CX0001] PIC16F631@SOIC20 [CX1033]  
PIC16F631@SOIC20(ISP) [CX0001] PIC16F631@SSOP20 [CX1070]  
PIC16F631@SSOP20(ISP) [CX0001] PIC16F636 [CX0001]  
PIC16F636(4-WORD PRO) [CX0001] PIC16F636(ISP) [CX0001]  
PIC16F636@QFN16 [CX4010]  
PIC16F636@QFN16(4-WORD PRO) [CX4010]  
PIC16F636@QFN16(ISP) [CX0001] PIC16F636@SOIC14 [CX1065]



PIC16F636@SOIC14(4-WORD PRO) [CX1065]  
PIC16F636@SOIC14(ISP) [CX0001] PIC16F636@TSSOP14 [CX1000]  
PIC16F636@TSSOP14(4-WORD PRO) [CX1000]  
PIC16F636@TSSOP14(ISP) [CX0001] PIC16F639 [CX0001]  
PIC16F639(ISP) [CX0001] PIC16F639@QFN20 [CX4011]  
PIC16F639@QFN20(ISP) [CX0001] PIC16F639@SOIC20 [CX1033]  
PIC16F639@SOIC20(ISP) [CX0001] PIC16F639@SSOP20 [CX1070]  
PIC16F639@SSOP20(ISP) [CX0001] PIC16F648A [CX0001]  
PIC16F648A(ISP) [CX0001] PIC16F648A@SOIC18 [CX1033]  
PIC16F648A@SOIC18(ISP) [CX0001] PIC16F648A@SSOP20 [CX1026]  
PIC16F648A@SSOP20(ISP) [CX0001] PIC16F676 [CX0001]  
PIC16F676(ISP) [CX0001] PIC16F676@SOIC14 [CX1065]  
PIC16F676@SOIC14(ISP) [CX0001] PIC16F676@TSSOP14 [CX1000]  
PIC16F676@TSSOP14(ISP) [CX0001] PIC16F677 [CX0001]  
PIC16F677(ISP) [CX0001] PIC16F677@QFN20 [CX4011]  
PIC16F677@QFN20(ISP) [CX0001] PIC16F677@SOIC20 [CX1033]  
PIC16F677@SOIC20(ISP) [CX0001] PIC16F677@SSOP20 [CX1070]  
PIC16F677@SSOP20(ISP) [CX0001] PIC16F684 [CX0001]  
PIC16F684(4-WORD PRO) [CX0001] PIC16F684(ISP) [CX0001]  
PIC16F684@QFN16 [CX4010]  
PIC16F684@QFN16(4-WORD PRO) [CX4010]  
PIC16F684@QFN16(ISP) [CX0001] PIC16F684@SOIC14 [CX1065]  
PIC16F684@SOIC14(4-WORD PRO) [CX1065]  
PIC16F684@SOIC14(ISP) [CX0001] PIC16F684@TSSOP14 [CX1000]  
PIC16F684@TSSOP14(4-WORD PRO) [CX1000]  
PIC16F684@TSSOP14(ISP) [CX0001] PIC16F685 [CX0001]  
PIC16F685(ISP) [CX0001] PIC16F685@QFN20 [CX4011]  
PIC16F685@QFN20(ISP) [CX0001] PIC16F685@SOIC20 [CX1033]  
PIC16F685@SOIC20(ISP) [CX0001] PIC16F685@SSOP20 [CX1070]  
PIC16F685@SSOP20(ISP) [CX0001] PIC16F687 [CX0001]  
PIC16F687(ISP) [CX0001] PIC16F687@QFN20 [CX4011]  
PIC16F687@QFN20(ISP) [CX0001] PIC16F687@SOIC20 [CX1033]  
PIC16F687@SOIC20(ISP) [CX0001] PIC16F687@SSOP20 [CX1070]  
PIC16F687@SSOP20(ISP) [CX0001] PIC16F688 [CX0001]  
PIC16F688(4-WORD PRO) [CX0001] PIC16F688(ISP) [CX0001]  
PIC16F688@QFN16 [CX4010]  
PIC16F688@QFN16(4-WORD PRO) [CX4010]  
PIC16F688@QFN16(ISP) [CX0001] PIC16F688@SOIC14 [CX1065]  
PIC16F688@SOIC14(4-WORD PRO) [CX1065]  
PIC16F688@SOIC14(ISP) [CX0001] PIC16F688@TSSOP14 [CX1000]  
PIC16F688@TSSOP14(4-WORD PRO) [CX1000]  
PIC16F688@TSSOP14(ISP) [CX0001] PIC16F689 [CX0001]  
PIC16F689(ISP) [CX0001] PIC16F689@QFN20 [CX4011]  
PIC16F689@QFN20(ISP) [CX0001] PIC16F689@SOIC20 [CX1033]  
PIC16F689@SOIC20(ISP) [CX0001] PIC16F689@SSOP20 [CX1070]  
PIC16F689@SSOP20(ISP) [CX0001] PIC16F690 [CX0001]  
PIC16F690(ISP) [CX0001] PIC16F690@QFN20 [CX4011]  
PIC16F690@QFN20(ISP) [CX0001] PIC16F690@SOIC20 [CX1033]  
PIC16F690@SOIC20(ISP) [CX0001] PIC16F690@SSOP20 [CX1070]  
PIC16F690@SSOP20(ISP) [CX0001]  
PIC16F690@SSOP20(REVRESE) [CX1070]  
PIC16F707 [CX0001] PIC16F707(ISP) [CX0001]  
PIC16F707@QFN44 [CX4019] PIC16F707@QFN44(ISP) [CX0001]  
PIC16F707@TQFP44 [CX3003] PIC16F707@TQFP44(ISP) [CX0001]  
PIC16F716 [CX0001] PIC16F716(4-WORD PRO) [CX0001]  
PIC16F716(ISP) [CX0001] PIC16F716@SOIC18 [CX1033]  
PIC16F716@SOIC18(4-WORD PRO) [CX1033]  
PIC16F716@SOIC18(ISP) [CX0001] PIC16F716@SSOP20 [CX1026]  
PIC16F716@SSOP20(4-WORD PRO) [CX1026]

PIC16F716@SSOP20(ISP) [CX0001]  
PIC16F72(ISP) [CX0001]  
PIC16F72@QFN28(ISP) [CX0001]  
PIC16F72@SOIC28(ISP) [CX0001]  
PIC16F72@SSOP28(ISP) [CX0001]  
PIC16F720@QFN20 [CX4011]  
PIC16F720@SSOP20 [CX1026]  
PIC16F721@QFN20 [CX4011]  
PIC16F721@SSOP20 [CX1026]  
PIC16F722(ISP) [CX0001]  
PIC16F722@QFN28(ISP) [CX0001]  
PIC16F722@SOIC28(ISP) [CX0001]  
PIC16F722@SSOP28(ISP) [CX0001]  
PIC16F722A(ISP) [CX0001]  
PIC16F722A@QFN28(ISP) [CX0001]  
PIC16F722A@SOIC28(ISP) [CX0001]  
PIC16F722A@SSOP28(ISP) [CX0001]  
PIC16F723(ISP) [CX0001]  
PIC16F723@QFN28(ISP) [CX0001]  
PIC16F723@SOIC28(ISP) [CX0001]  
PIC16F723@SSOP28(ISP) [CX0001]  
PIC16F723A(ISP) [CX0001]  
PIC16F723A@QFN28(ISP) [CX0001]  
PIC16F723A@SOIC28(ISP) [CX0001]  
PIC16F723A@SSOP28(ISP) [CX0001]  
PIC16F724(ISP) [CX0001]  
PIC16F724@QFN44(ISP) [CX0001]  
PIC16F724@TQFP44(ISP) [CX0001]  
PIC16F726(ISP) [CX0001]  
PIC16F726@QFN28(ISP) [CX0001]  
PIC16F726@SOIC28(ISP) [CX0001]  
PIC16F726@SSOP28(ISP) [CX0001]  
PIC16F727(ISP) [CX0001]  
PIC16F727@QFN44(ISP) [CX0001]  
PIC16F727@TQFP44(ISP) [CX0001]  
PIC16F73(ISP) [CX0001]  
PIC16F73@SOIC28 [CX1033]  
PIC16F73@SSOP28 [CX1026]  
PIC16F737 [CX0001]  
PIC16F737@SOIC28 [CX1033]  
PIC16F737@SSOP28 [CX1077]  
PIC16F74 [CX0001]  
PIC16F74@PLCC44 [CX2044]  
PIC16F74@TQFP44 [CX3003]  
PIC16F747 [CX0001]  
PIC16F747@TQFP44 [CX3003]  
PIC16F76 [CX0001]  
PIC16F76@QFN28 [CX4014]  
PIC16F76@SOIC28(ISP) [CX0001]  
PIC16F76@SSOP28(ISP) [CX0001]  
PIC16F767(ISP) [CX0001]  
PIC16F767@SOIC28(ISP) [CX0001]  
PIC16F767@SSOP28(ISP) [CX0001]  
PIC16F77(ISP) [CX0001]  
PIC16F77@PLCC44(ISP) [CX0001]  
PIC16F77@TQFP44(ISP) [CX0001]  
PIC16F777(ISP) [CX0001]  
PIC16F777@TQFP44(ISP) [CX0001]  
PIC16F785(ISP) [CX0001]

PIC16F72 [CX0001]  
PIC16F72@QFN28 [CX4014]  
PIC16F72@SOIC28 [CX1033]  
PIC16F72@SSOP28 [CX1026]  
PIC16F720 [CX0001]  
PIC16F720@SOIC20 [CX1033]  
PIC16F721 [CX0001]  
PIC16F721@SOIC20 [CX1033]  
PIC16F722 [CX0001]  
PIC16F722@QFN28 [CX4014]  
PIC16F722@SOIC28 [CX1033]  
PIC16F722@SSOP28 [CX1077]  
PIC16F722A [CX0001]  
PIC16F722A@QFN28 [CX4014]  
PIC16F722A@SOIC28 [CX1033]  
PIC16F722A@SSOP28 [CX1077]  
PIC16F723 [CX0001]  
PIC16F723@QFN28 [CX4014]  
PIC16F723@SOIC28 [CX1033]  
PIC16F723@SSOP28 [CX1077]  
PIC16F723A [CX0001]  
PIC16F723A@QFN28 [CX4014]  
PIC16F723A@SOIC28 [CX1033]  
PIC16F723A@SSOP28 [CX1077]  
PIC16F724 [CX0001]  
PIC16F724@QFN44 [CX4019]  
PIC16F724@TQFP44 [CX3003]  
PIC16F726 [CX0001]  
PIC16F726@QFN28 [CX4014]  
PIC16F726@SOIC28 [CX1033]  
PIC16F726@SSOP28 [CX1077]  
PIC16F727 [CX0001]  
PIC16F727@QFN44 [CX4019]  
PIC16F727@TQFP44 [CX3003]  
PIC16F73 [CX0001]  
PIC16F73@QFN28 [CX4014]  
PIC16F73@SOIC28(ISP) [CX0001]  
PIC16F73@SSOP28(ISP) [CX0001]  
PIC16F737(ISP) [CX0001]  
PIC16F737@SOIC28(ISP) [CX0001]  
PIC16F737@SSOP28(ISP) [CX0001]  
PIC16F74(ISP) [CX0001]  
PIC16F74@PLCC44(ISP) [CX0001]  
PIC16F74@TQFP44(ISP) [CX0001]  
PIC16F747(ISP) [CX0001]  
PIC16F747@TQFP44(ISP) [CX0001]  
PIC16F76(ISP) [CX0001]  
PIC16F76@SOIC28 [CX1033]  
PIC16F76@SSOP28 [CX1026]  
PIC16F767 [CX0001]  
PIC16F767@SOIC28 [CX1033]  
PIC16F767@SSOP28 [CX1077]  
PIC16F77 [CX0001]  
PIC16F77@PLCC44 [CX2044]  
PIC16F77@TQFP44 [CX3003]  
PIC16F777 [CX0001]  
PIC16F777@TQFP44 [CX3003]  
PIC16F785 [CX0001]  
PIC16F785@QFN20 [CX4011]

PIC16F785@QFN20(ISP) [CX0001]	PIC16F785@SOIC20 [CX1033]
PIC16F785@SOIC20(ISP) [CX0001]	PIC16F785@SSOP20 [CX1026]
PIC16F785@SSOP20(ISP) [CX0001]	PIC16F818 [CX0001]
PIC16F818(ISP) [CX0001]	PIC16F818@QFN28 [CX4014]
PIC16F818@QFN28(ISP) [CX0001]	PIC16F818@SOIC18 [CX1033]
PIC16F818@SOIC18(ISP) [CX0001]	PIC16F818@SSOP20 [CX1026]
PIC16F818@SSOP20(ISP) [CX0001]	PIC16F819 [CX0001]
PIC16F819(ISP) [CX0001]	PIC16F819@QFN28 [CX4014]
PIC16F819@QFN28(ISP) [CX0001]	PIC16F819@SOIC18 [CX1033]
PIC16F819@SOIC18(ISP) [CX0001]	PIC16F819@SSOP20 [CX1026]
PIC16F819@SSOP20(ISP) [CX0001]	PIC16F83 [CX0001]
PIC16F83(ISP) [CX0001]	PIC16F83@SOIC18 [CX1033]
PIC16F83@SOIC18(ISP) [CX0001]	PIC16F84 [CX0001]
PIC16F84(ISP) [CX0001]	PIC16F84@SOIC18 [CX1033]
PIC16F84@SOIC18(ISP) [CX0001]	PIC16F84A [CX0001]
PIC16F84A(ISP) [CX0001]	PIC16F84A@SOIC18 [CX1033]
PIC16F84A@SOIC18(ISP) [CX0001]	PIC16F84A@SSOP20 [CX1026]
PIC16F84A@SSOP20(ISP) [CX0001]	PIC16F87 [CX0001]
PIC16F87(ISP) [CX0001]	PIC16F87@QFN28 [CX4014]
PIC16F87@QFN28(ISP) [CX0001]	PIC16F87@SOIC18 [CX1033]
PIC16F87@SOIC18(ISP) [CX0001]	PIC16F87@SSOP20 [CX1026]
PIC16F87@SSOP20(ISP) [CX0001]	PIC16F870 [CX0001]
PIC16F870(ISP) [CX0001]	PIC16F870@SOIC28 [CX1033]
PIC16F870@SOIC28(ISP)	PIC16F870@SSOP28 [CX1026]
PIC16F870@SSOP28(ISP)	PIC16F871 [CX0001]
PIC16F871(ISP)	PIC16F871@MQFP44 [CX3088]
PIC16F871@MQFP44(ISP)	PIC16F871@PLCC44 [CX2044]
PIC16F871@PLCC44(ISP)	PIC16F871@TQFP44 [CX3003]
PIC16F871@TQFP44(ISP)	PIC16F872 [CX0001]
PIC16F872(ISP)	PIC16F872@SOIC28 [CX1033]
PIC16F872@SOIC28(ISP)	PIC16F872@SSOP28 [CX1026]
PIC16F872@SSOP28(ISP)	PIC16F873 [CX0001]
PIC16F873(ISP)	PIC16F873@SOIC28 [CX1033]
PIC16F873@SOIC28(ISP)	PIC16F873A [CX0001]
PIC16F873A(ISP)(High-V) [CX0001]	PIC16F873A(ISP)(Low-V) [CX0001]
PIC16F873A(ISP3.3v)(HV) [CX0001]	PIC16F873A(ISP3.3v)(LV) [CX0001]
PIC16F873A@QFN28 [CX4014]	
PIC16F873A@QFN28(ISP)(High-V) [CX0001]	
PIC16F873A@QFN28(ISP)(Low-V) [CX0001]	
PIC16F873A@QFN28(ISP3.3v)(HV) [CX0001]	
PIC16F873A@QFN28(ISP3.3v)(LV) [CX0001]	
PIC16F873A@SOIC28 [CX1033]	
PIC16F873A@SOIC28(ISP)(High-V) [CX0001]	
PIC16F873A@SOIC28(ISP)(Low-V) [CX0001]	
PIC16F873A@SOIC28(ISP3.3v)(HV) [CX0001]	
PIC16F873A@SOIC28(ISP3.3v)(LV) [CX0001]	
PIC16F873A@SSOP28 [CX1026]	
PIC16F873A@SSOP28(ISP)(High-V) [CX0001]	
PIC16F873A@SSOP28(ISP)(Low-V) [CX0001]	
PIC16F873A@SSOP28(ISP3.3v)(HV) [CX0001]	
PIC16F873A@SSOP28(ISP3.3v)(LV) [CX0001]	
PIC16F874 [CX0001]	PIC16F874(ISP)
PIC16F874@MQFP44 [CX3088]	PIC16F874@MQFP44(ISP)
PIC16F874@PLCC44 [CX2044]	PIC16F874@PLCC44(ISP)
PIC16F874@TQFP44 [CX3003]	PIC16F874@TQFP44(ISP)
PIC16F874A [CX0001]	PIC16F874A(ISP)(High-V) [CX0001]
PIC16F874A(ISP)(Low-V) [CX0001]	PIC16F874A(ISP3.3v)(HV) [CX0001]
PIC16F874A(ISP3.3v)(LV) [CX0001]	PIC16F874A@PLCC44 [CX2044]
PIC16F874A@PLCC44(ISP)(High-V) [CX0001]	

PIC16F874A@PLCC44(ISP)(Low-V) [CX0001]  
PIC16F874A@PLCC44(ISP3.3v)(HV) [CX0001]  
PIC16F874A@PLCC44(ISP3.3v)(LV) [CX0001]  
PIC16F874A@TQFP44 [CX3003]  
PIC16F874A@TQFP44(ISP)(High-V) [CX0001]  
PIC16F874A@TQFP44(ISP)(Low-V) [CX0001]  
PIC16F874A@TQFP44(ISP3.3v)(HV) [CX0001]  
PIC16F874A@TQFP44(ISP3.3v)(LV) [CX0001]  
PIC16F876 [CX0001] PIC16F876(ISP)  
PIC16F876@SOIC28 [CX1033] PIC16F876@SOIC28(ISP)  
PIC16F876A [CX0001] PIC16F876A(ISP)(High-V) [CX0001]  
PIC16F876A(ISP)(Low-V) [CX0001] PIC16F876A(ISP3.3v)(HV) [CX0001]  
PIC16F876A(ISP3.3v)(LV) [CX0001] PIC16F876A@QFN28 [CX4014]  
PIC16F876A@QFN28(ISP)(High-V) [CX0001]  
PIC16F876A@QFN28(ISP)(Low-V) [CX0001]  
PIC16F876A@QFN28(ISP3.3v)(HV) [CX0001]  
PIC16F876A@QFN28(ISP3.3v)(LV) [CX0001]  
PIC16F876A@SOIC28 [CX1033]  
PIC16F876A@SOIC28(ISP)(High-V) [CX0001]  
PIC16F876A@SOIC28(ISP)(Low-V) [CX0001]  
PIC16F876A@SOIC28(ISP3.3v)(HV) [CX0001]  
PIC16F876A@SOIC28(ISP3.3v)(LV) [CX0001]  
PIC16F876A@SSOP28 [CX1026]  
PIC16F876A@SSOP28(ISP)(High-V) [CX0001]  
PIC16F876A@SSOP28(ISP)(Low-V) [CX0001]  
PIC16F876A@SSOP28(ISP3.3v)(HV) [CX0001]  
PIC16F876A@SSOP28(ISP3.3v)(LV) [CX0001]  
PIC16F877 [CX0001] PIC16F877(ISP)  
PIC16F877@MQFP44 [CX3088] PIC16F877@MQFP44(ISP)  
PIC16F877@PLCC44 [CX2044] PIC16F877@PLCC44(ISP)  
PIC16F877@TQFP44 [CX3003] PIC16F877@TQFP44(ISP)  
PIC16F877A [CX0001] PIC16F877A(ISP)(High-V) [CX0001]  
PIC16F877A(ISP)(Low-V) [CX0001] PIC16F877A(ISP3.3v)(HV) [CX0001]  
PIC16F877A(ISP3.3v)(LV) [CX0001] PIC16F877A@PLCC44 [CX2044]  
PIC16F877A@PLCC44(ISP)(High-V) [CX0001]  
PIC16F877A@PLCC44(ISP)(Low-V) [CX0001]  
PIC16F877A@PLCC44(ISP3.3v)(HV) [CX0001]  
PIC16F877A@PLCC44(ISP3.3v)(LV) [CX0001]  
PIC16F877A@TQFP44 [CX3003]  
PIC16F877A@TQFP44(ISP)(High-V) [CX0001]  
PIC16F877A@TQFP44(ISP)(Low-V) [CX0001]  
PIC16F877A@TQFP44(ISP3.3v)(HV) [CX0001]  
PIC16F877A@TQFP44(ISP3.3v)(LV) [CX0001]  
PIC16F88 [CX0001] PIC16F88(ISP) [CX0001]  
PIC16F88@QFN28 [CX4014] PIC16F88@QFN28(ISP) [CX0001]  
PIC16F88@SOIC18 [CX1033] PIC16F88@SOIC18(ISP) [CX0001]  
PIC16F88@SSOP20 [CX1026] PIC16F88@SSOP20(ISP) [CX0001]  
PIC16F882 [CX0001] PIC16F882(ISP)(High-V) [CX0001]  
PIC16F882(ISP)(Low-V) [CX0001] PIC16F882@QFN28 [CX4014]  
PIC16F882@QFN28(ISP)(High-V) [CX0001]  
PIC16F882@QFN28(ISP)(Low-V) [CX0001]  
PIC16F882@SOIC28 [CX1033]  
PIC16F882@SOIC28(ISP)(High-V) [CX0001]  
PIC16F882@SOIC28(ISP)(Low-V) [CX0001]  
PIC16F882@SSOP28 [CX1026]  
PIC16F882@SSOP28(ISP)(High-V) [CX0001]  
PIC16F882@SSOP28(ISP)(Low-V) [CX0001]  
PIC16F883 [CX0001] PIC16F883(ISP)(High-V) [CX0001]  
PIC16F883(ISP)(Low-V) [CX0001] PIC16F883@QFN28 [CX4014]

PIC16F883@QFN28(ISP)(High-V) [CX0001]  
PIC16F883@QFN28(ISP)(Low-V) [CX0001]  
PIC16F883@SOIC28 [CX1033]  
PIC16F883@SOIC28(ISP)(High-V) [CX0001]  
PIC16F883@SOIC28(ISP)(Low-V) [CX0001]  
PIC16F883@SSOP28 [CX1026]  
PIC16F883@SSOP28(ISP)(High-V) [CX0001]  
PIC16F883@SSOP28(ISP)(Low-V) [CX0001]  
PIC16F884 [CX0001] PIC16F884(ISP)(High-V) [CX0001]  
PIC16F884(ISP)(Low-V) [CX0001] PIC16F884@QFN44 [CX4018]  
PIC16F884@QFN44(ISP)(High-V) [CX0001]  
PIC16F884@QFN44(ISP)(Low-V) [CX0001]  
PIC16F884@QFN44(ML) [CX4019]  
PIC16F884@QFN44(ML)(ISP)(High-V) [CX0001]  
PIC16F884@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC16F884@TQFP44 [CX3003]  
PIC16F884@TQFP44(ISP)(High-V) [CX0001]  
PIC16F884@TQFP44(ISP)(Low-V) [CX0001]  
PIC16F886 [CX0001] PIC16F886(ISP)(High-V) [CX0001]  
PIC16F886(ISP)(Low-V) [CX0001] PIC16F886@QFN28 [CX4014]  
PIC16F886@QFN28(ISP)(High-V) [CX0001]  
PIC16F886@QFN28(ISP)(Low-V) [CX0001]  
PIC16F886@SOIC28 [CX1033]  
PIC16F886@SOIC28(ISP)(High-V) [CX0001]  
PIC16F886@SOIC28(ISP)(Low-V) [CX0001]  
PIC16F886@SSOP28 [CX1026]  
PIC16F886@SSOP28(ISP)(High-V) [CX0001]  
PIC16F886@SSOP28(ISP)(Low-V) [CX0001]  
PIC16F887 [CX0001] PIC16F887(ISP)(High-V) [CX0001]  
PIC16F887(ISP)(Low-V) [CX0001] PIC16F887@QFN44 [CX4018]  
PIC16F887@QFN44(ISP)(High-V) [CX0001]  
PIC16F887@QFN44(ISP)(Low-V) [CX0001]  
PIC16F887@QFN44(ML) [CX4019]  
PIC16F887@QFN44(ML)(ISP)(High-V) [CX0001]  
PIC16F887@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC16F887@TQFP44 [CX3003]  
PIC16F887@TQFP44(ISP)(High-V) [CX0001]  
PIC16F887@TQFP44(ISP)(Low-V) [CX0001]  
PIC16F913 [CX0001] PIC16F913(ISP) [CX0001]  
PIC16F913@QFN28 [CX4014] PIC16F913@QFN28(ISP) [CX0001]  
PIC16F913@SOIC28 [CX1033] PIC16F913@SOIC28(ISP) [CX0001]  
PIC16F913@SSOP28 [CX1026] PIC16F913@SSOP28(ISP) [CX0001]  
PIC16F914 [CX0001] PIC16F914(ISP) [CX0001]  
PIC16F914@QFN44 [CX4018] PIC16F914@QFN44(ISP) [CX0001]  
PIC16F914@QFN44(ML) [CX4019]  
PIC16F914@QFN44(ML)(ISP) [CX0001]  
PIC16F914@TQFP44 [CX3003] PIC16F914@TQFP44(ISP) [CX0001]  
PIC16F916 [CX0001] PIC16F916(ISP) [CX0001]  
PIC16F916@QFN28 [CX4014] PIC16F916@QFN28(ISP) [CX0001]  
PIC16F916@SOIC28 [CX1033] PIC16F916@SOIC28(ISP) [CX0001]  
PIC16F916@SSOP28 [CX1026] PIC16F916@SSOP28(ISP) [CX0001]  
PIC16F917 [CX0001] PIC16F917(ISP) [CX0001]  
PIC16F917@QFN44 [CX4018] PIC16F917@QFN44(ISP) [CX0001]  
PIC16F917@QFN44(ML) [CX4019]  
PIC16F917@QFN44(ML)(ISP) [CX0001]  
PIC16F917@TQFP44 [CX3003] PIC16F917@TQFP44(ISP) [CX0001]  
PIC16F946@TQFP64 [CX3011] PIC16F946@TQFP64(ISP) [CX0001]  
PIC16HV540 [CX0001] PIC16HV540@SOIC18 [CX1033]  
PIC16HV540@SSOP20 [CX1026] PIC16HV610 [CX0001]

PIC16HV610(ISP) [CX0001]  
PIC16HV610@QFN16(ISP) [CX0001]  
PIC16HV610@SOIC14(ISP) [CX0001]  
PIC16HV610@TSSOP14(ISP) [CX0001]  
PIC16HV616(ISP) [CX0001]  
PIC16HV616@QFN16(ISP) [CX0001]  
PIC16HV616@SOIC14(ISP) [CX0001]  
PIC16HV616@TSSOP14(ISP) [CX0001]  
PIC16HV785(ISP) [CX0001]  
PIC16HV785@QFN20(ISP) [CX0001]  
PIC16HV785@SOIC20(ISP) [CX0001]  
PIC16HV785@SSOP20(ISP) [CX0001]  
PIC16LC505@SOIC14 [CX1016]  
PIC16LC54A@SOIC18 [CX1033]  
PIC16LC54C [CX0001]  
PIC16LC54C@SSOP20 [CX1026]  
PIC16LC554(ISP) [CX0001]  
PIC16LC554@SOIC18(ISP) [CX0001]  
PIC16LC558(ISP) [CX0001]  
PIC16LC558@SOIC18(ISP) [CX0001]  
PIC16LC56A@SOIC18 [CX1033]  
PIC16LC58A [CX0001]  
PIC16LC58A@SSOP20 [CX1026]  
PIC16LC58B@SOIC18 [CX1033]  
PIC16LC620 [CX0001]  
PIC16LC620@SOIC18 [CX1033]  
PIC16LC620A [CX0001]  
PIC16LC620A@SOIC18 [CX1033]  
PIC16LC620A@SSOP20 [CX1026]  
PIC16LC621A [CX0001]  
PIC16LC621A@SOIC18 [CX1033]  
PIC16LC621A@SSOP20 [CX1026]  
PIC16LC622 [CX0001]  
PIC16LC622@SOIC18 [CX1033]  
PIC16LC62A [CX0001]  
PIC16LC62A@SOIC28 [CX1033]  
PIC16LC62A@SSOP28 [CX1026]  
PIC16LC62B [CX0001]  
PIC16LC62B@SOIC28 [CX1033]  
PIC16LC62B@SSOP28 [CX1026]  
PIC16LC63 [CX0001]  
PIC16LC63@SOIC28 [CX1033]  
PIC16LC63A [CX0001]  
PIC16LC63A@SOIC28 [CX1033]  
PIC16LC63A@SSOP28 [CX1026]  
PIC16LC64A [CX0001]  
PIC16LC64A@PLCC44 [CX2044]  
PIC16LC64A@TQFP44 [CX3003]  
PIC16LC65A [CX0001]  
PIC16LC65A@PLCC44 [CX2044]  
PIC16LC65A@TQFP44 [CX3003]  
PIC16LC65B [CX0001]  
PIC16LC65B@PLCC44 [CX2044]  
PIC16LC65B@TQFP44 [CX3003]  
PIC16LC66 [CX0001]  
PIC16LC66@SOIC28 [CX1033]  
PIC16LC67 [CX0001]  
PIC16LC67@PLCC44 [CX2044]  
PIC16LC67@TQFP44 [CX3003]  
PIC16HV610@QFN16 [CX4010]  
PIC16HV610@SOIC14 [CX1016]  
PIC16HV610@TSSOP14 [CX1000]  
PIC16HV616 [CX0001]  
PIC16HV616@QFN16 [CX4010]  
PIC16HV616@SOIC14 [CX1016]  
PIC16HV616@TSSOP14 [CX1000]  
PIC16HV785 [CX0001]  
PIC16HV785@QFN20 [CX4011]  
PIC16HV785@SOIC20 [CX1033]  
PIC16HV785@SSOP20 [CX1026]  
PIC16LC505 [CX0001]  
PIC16LC54A [CX0001]  
PIC16LC54A@SSOP20 [CX1026]  
PIC16LC54C@SOIC18 [CX1033]  
PIC16LC554 [CX0001]  
PIC16LC554@SOIC18 [CX1033]  
PIC16LC558 [CX0001]  
PIC16LC558@SOIC18 [CX1033]  
PIC16LC56A [CX0001]  
PIC16LC56A@SSOP20 [CX1026]  
PIC16LC58A@SOIC18 [CX1033]  
PIC16LC58B [CX0001]  
PIC16LC58B@SSOP20 [CX1026]  
PIC16LC620(ISP) [CX0001]  
PIC16LC620@SOIC18(ISP) [CX0001]  
PIC16LC620A(ISP) [CX0001]  
PIC16LC620A@SOIC18(ISP) [CX0001]  
PIC16LC620A@SSOP20(ISP) [CX0001]  
PIC16LC621A(ISP) [CX0001]  
PIC16LC621A@SOIC18(ISP) [CX0001]  
PIC16LC621A@SSOP20(ISP) [CX0001]  
PIC16LC622(ISP) [CX0001]  
PIC16LC622@SOIC18(ISP) [CX0001]  
PIC16LC62A(ISP) [CX0001]  
PIC16LC62A@SOIC28(ISP) [CX0001]  
PIC16LC62A@SSOP28(ISP) [CX0001]  
PIC16LC62B(ISP) [CX0001]  
PIC16LC62B@SOIC28(ISP) [CX0001]  
PIC16LC62B@SSOP28(ISP) [CX0001]  
PIC16LC63(ISP) [CX0001]  
PIC16LC63@SOIC28(ISP) [CX0001]  
PIC16LC63A(ISP) [CX0001]  
PIC16LC63A@SOIC28(ISP) [CX0001]  
PIC16LC63A@SSOP28(ISP) [CX0001]  
PIC16LC64A(ISP) [CX0001]  
PIC16LC64A@PLCC44(ISP) [CX0001]  
PIC16LC64A@TQFP44(ISP) [CX0001]  
PIC16LC65A(ISP) [CX0001]  
PIC16LC65A@PLCC44(ISP) [CX0001]  
PIC16LC65A@TQFP44(ISP) [CX0001]  
PIC16LC65B(ISP) [CX0001]  
PIC16LC65B@PLCC44(ISP) [CX0001]  
PIC16LC65B@TQFP44(ISP) [CX0001]  
PIC16LC66(ISP) [CX0001]  
PIC16LC66@SOIC28(ISP) [CX0001]  
PIC16LC67(ISP) [CX0001]  
PIC16LC67@PLCC44(ISP) [CX0001]  
PIC16LC67@TQFP44(ISP) [CX0001]

PIC16LC71 [CX0001]  
PIC16LC71@SOIC18 [CX1033]  
PIC16LC710 [CX0001]  
PIC16LC710@SOIC18 [CX1033]  
PIC16LC710@SSOP20 [CX1026]  
PIC16LC711 [CX0001]  
PIC16LC711@SOIC18 [CX1033]  
PIC16LC711@SSOP20 [CX1026]  
PIC16LC712 [CX0001]  
PIC16LC712@SOIC18 [CX1033]  
PIC16LC712@SSOP20 [CX1026]  
PIC16LC715 [CX0001]  
PIC16LC716 [CX0001]  
PIC16LC716@SOIC18 [CX1033]  
PIC16LC716@SSOP20 [CX1026]  
PIC16LC717 [CX0001]  
PIC16LC717@SOIC18  
PIC16LC717@SSOP20 [CX1026]  
PIC16LC72 [CX0001]  
PIC16LC72@SOIC28 [CX1033]  
PIC16LC72@SSOP28 [CX1026]  
PIC16LC72A [CX0001]  
PIC16LC72A@SOIC28 [CX1033]  
PIC16LC72A@SSOP28 [CX1026]  
PIC16LC73A [CX0001]  
PIC16LC73A@SOIC28 [CX1033]  
PIC16LC73B [CX0001]  
PIC16LC73B@SOIC28 [CX1033]  
PIC16LC73B@SSOP28 [CX1026]  
PIC16LC74 [CX0001]  
PIC16LC74@PLCC44 [CX2044]  
PIC16LC74@TQFP44 [CX3003]  
PIC16LC74A [CX0001]  
PIC16LC74A@PLCC44 [CX2044]  
PIC16LC74A@TQFP44 [CX3003]  
PIC16LC74B [CX0001]  
PIC16LC74B@MQFP44 [CX3002]  
PIC16LC74B@PLCC44 [CX2044]  
PIC16LC74B@TQFP44 [CX3003]  
PIC16LC76 [CX0001]  
PIC16LC76@SOIC28 [CX1033]  
PIC16LC77 [CX0001]  
PIC16LC77@PLCC44 [CX2044]  
PIC16LC773 [CX0001]  
PIC16LC773@SOIC28  
PIC16LC773@SSOP28 [CX1026]  
PIC16LC774 [CX0001]  
PIC16LC774@PLCC44 [CX2044]  
PIC16LC774@TQFP44 [CX3003]  
PIC16LC84 [CX0001]  
PIC16LC84@SOIC18 [CX1033]  
PIC16LC923@PLCC68 [CX2068]  
PIC16LC923@SDIP64 [CX0064]  
PIC16LC923@TQFP64 [CX3011]  
PIC16LC924@PLCC68 [CX2068]  
PIC16LC924@SDIP64 [CX0064]  
PIC16LC924@TQFP64 [CX3011]  
PIC16LC925@PLCC68 [CX2068]  
PIC16LC925@TQFP64 [CX3011]

PIC16LC71(ISP) [CX0001]  
PIC16LC71@SOIC18(ISP) [CX0001]  
PIC16LC710(ISP) [CX0001]  
PIC16LC710@SOIC18(ISP) [CX0001]  
PIC16LC710@SSOP20(ISP) [CX0001]  
PIC16LC711(ISP) [CX0001]  
PIC16LC711@SOIC18(ISP) [CX0001]  
PIC16LC711@SSOP20(ISP) [CX0001]  
PIC16LC712(ISP) [CX0001]  
PIC16LC712@SOIC18(ISP) [CX0001]  
PIC16LC712@SSOP20(ISP) [CX0001]  
PIC16LC715@SOIC18 [CX1033]  
PIC16LC716(ISP) [CX0001]  
PIC16LC716@SOIC18(ISP) [CX0001]  
PIC16LC716@SSOP20(ISP) [CX0001]  
PIC16LC717(ISP) [CX0001]  
PIC16LC717@SOIC18(ISP) [CX0001]  
PIC16LC717@SSOP20(ISP) [CX0001]  
PIC16LC72(ISP) [CX0001]  
PIC16LC72@SOIC28(ISP) [CX0001]  
PIC16LC72@SSOP28(ISP) [CX0001]  
PIC16LC72A(ISP) [CX0001]  
PIC16LC72A@SOIC28(ISP) [CX0001]  
PIC16LC72A@SSOP28(ISP) [CX0001]  
PIC16LC73A(ISP) [CX0001]  
PIC16LC73A@SOIC28(ISP) [CX0001]  
PIC16LC73B(ISP) [CX0001]  
PIC16LC73B@SOIC28(ISP) [CX0001]  
PIC16LC73B@SSOP28(ISP) [CX0001]  
PIC16LC74(ISP) [CX0001]  
PIC16LC74@PLCC44(ISP) [CX0001]  
PIC16LC74@TQFP44(ISP) [CX0001]  
PIC16LC74A(ISP) [CX0001]  
PIC16LC74A@PLCC44(ISP) [CX0001]  
PIC16LC74A@TQFP44(ISP) [CX0001]  
PIC16LC74B(ISP) [CX0001]  
PIC16LC74B@MQFP44(ISP) [CX0001]  
PIC16LC74B@PLCC44(ISP) [CX0001]  
PIC16LC74B@TQFP44(ISP) [CX0001]  
PIC16LC76(ISP) [CX0001]  
PIC16LC76@SOIC28(ISP) [CX0001]  
PIC16LC77(ISP) [CX0001]  
PIC16LC77@PLCC44(ISP) [CX0001]  
PIC16LC773(ISP) [CX0001]  
PIC16LC773@SOIC28(ISP) [CX0001]  
PIC16LC773@SSOP28(ISP) [CX0001]  
PIC16LC774(ISP) [CX0001]  
PIC16LC774@PLCC44(ISP) [CX0001]  
PIC16LC774@TQFP44(ISP) [CX0001]  
PIC16LC84(ISP) [CX0001]  
PIC16LC84@SOIC18(ISP) [CX0001]  
PIC16LC923@PLCC68(ISP) [CX0001]  
PIC16LC923@SDIP64(ISP) [CX0001]  
PIC16LC923@TQFP64(ISP) [CX0001]  
PIC16LC924@PLCC68(ISP) [CX0001]  
PIC16LC924@SDIP64(ISP) [CX0001]  
PIC16LC924@TQFP64(ISP) [CX0001]  
PIC16LC925@PLCC68(ISP) [CX0001]  
PIC16LC925@TQFP64(ISP) [CX0001]

PIC16LC926@PLCC68 [CX2068]  
PIC16LC926@TQFP64 [CX3011]  
PIC16LCE623@SOIC18 [CX1033]  
PIC16LCE623@SSOP20 [CX1026]  
PIC16LF1454 [CX0001]  
PIC16LF1454@QFN16 [CX4010]  
PIC16LF1454@TSSOP14 [CX1000]  
PIC16LF1455(ISP) [CX0001]  
PIC16LF1455@SOIC14 [CX1016]  
PIC16LF1458 [CX0001]  
PIC16LF1458@QFN20 [CX4011]  
PIC16LF1458@SSOP20 [CX1026]  
PIC16LF1459(ISP) [CX0001]  
PIC16LF1459@SOIC20 [CX1033]  
PIC16LF1503 [CX0001]  
PIC16LF1503@QFN16 [CX4053]  
PIC16LF1503@SOIC14 [CX1016]  
PIC16LF1503@TSOP14 [CX1000]  
PIC16LF1503@TSSOP14(ISP) [CX0001]  
PIC16LF1507 [CX0001]  
PIC16LF1507@QFN20 [CX4011]  
PIC16LF1507@SOIC20 [CX1033]  
PIC16LF1507@SSOP20 [CX1026]  
PIC16LF1508 [CX0001]  
PIC16LF1508@QFN20 [CX4011]  
PIC16LF1508@SOIC20 [CX1033]  
PIC16LF1508@SSOP20 [CX1026]  
PIC16LF1509 [CX0001]  
PIC16LF1509@QFN20 [CX4011]  
PIC16LF1509@SOIC20 [CX1033]  
PIC16LF1509@SSOP20 [CX1026]  
PIC16LF1512 [CX0001]  
PIC16LF1512@SOIC18(ISP) [CX0001]  
PIC16LF1512@SSOP28 [CX1026]  
PIC16LF1512@UQFN28 [CX4036]  
PIC16LF1513 [CX0001]  
PIC16LF1513@SOIC18(ISP) [CX0001]  
PIC16LF1513@SSOP28 [CX1026]  
PIC16LF1513@UQFN28 [CX4036]  
PIC16LF1516 [CX0001]  
PIC16LF1516@SOIC18(ISP) [CX0001]  
PIC16LF1516@SSOP28 [CX1026]  
PIC16LF1516@UQFN28 [CX4036]  
PIC16LF1517 [CX0001]  
PIC16LF1517@TQFP44 [CX3003]  
PIC16LF1517@UQFN40 [CX4039]  
PIC16LF1518 [CX0001]  
PIC16LF1518@SOIC18(ISP) [CX0001]  
PIC16LF1518@SSOP28 [CX1026]  
PIC16LF1518@UQFN28 [CX4036]  
PIC16LF1519 [CX0001]  
PIC16LF1519@TQFP44 [CX3003]  
PIC16LF1519@UQFN40 [CX4039]  
PIC16LF1526@QFN64 [CX3011]  
PIC16LF1526@TQFP64 [CX3011]  
PIC16LF1527@QFN64 [CX3011]  
PIC16LF1527@TQFP64 [CX3011]  
PIC16LF1782 [CX0001]  
PIC16LF1782@SOIC28 [CX1033]

PIC16LC926@PLCC68(ISP) [CX0001]  
PIC16LC926@TQFP64(ISP) [CX0001]  
PIC16LCE623@SOIC18(ISP) [CX0001]  
PIC16LCE623@SSOP20(ISP) [CX0001]  
PIC16LF1454(ISP) [CX0001]  
PIC16LF1454@SOIC14 [CX1016]  
PIC16LF1455 [CX0001]  
PIC16LF1455@QFN16 [CX4010]  
PIC16LF1455@TSSOP14 [CX1000]  
PIC16LF1458(ISP) [CX0001]  
PIC16LF1458@SOIC20 [CX1033]  
PIC16LF1459 [CX0001]  
PIC16LF1459@QFN20 [CX4011]  
PIC16LF1459@SSOP20 [CX1026]  
PIC16LF1503(ISP) [CX0001]  
PIC16LF1503@QFN16(ISP) [CX0001]  
PIC16LF1503@SOIC14(ISP) [CX0001]  
PIC16LF1507(ISP) [CX0001]  
PIC16LF1507@QFN20(ISP) [CX0001]  
PIC16LF1507@SOIC20(ISP) [CX0001]  
PIC16LF1507@SSOP20(ISP) [CX0001]  
PIC16LF1508(ISP) [CX0001]  
PIC16LF1508@QFN20(ISP) [CX0001]  
PIC16LF1508@SOIC20(ISP) [CX0001]  
PIC16LF1508@SSOP20(ISP) [CX0001]  
PIC16LF1509(ISP) [CX0001]  
PIC16LF1509@QFN20(ISP) [CX0001]  
PIC16LF1509@SOIC20(ISP) [CX0001]  
PIC16LF1509@SSOP20(ISP) [CX0001]  
PIC16LF1512(ISP) [CX0001]  
PIC16LF1512@SOIC28 [CX1033]  
PIC16LF1512@SSOP28(ISP) [CX0001]  
PIC16LF1512@UQFN28(ISP) [CX0001]  
PIC16LF1513(ISP) [CX0001]  
PIC16LF1513@SOIC28 [CX1033]  
PIC16LF1513@SSOP28(ISP) [CX0001]  
PIC16LF1513@UQFN28(ISP) [CX0001]  
PIC16LF1516(ISP) [CX0001]  
PIC16LF1516@SOIC28 [CX1033]  
PIC16LF1516@SSOP28(ISP) [CX0001]  
PIC16LF1516@UQFN28(ISP) [CX0001]  
PIC16LF1517(ISP) [CX0001]  
PIC16LF1517@TQFP44(ISP) [CX0001]  
PIC16LF1517@UQFN40(ISP) [CX0001]  
PIC16LF1518(ISP) [CX0001]  
PIC16LF1518@SOIC28 [CX1033]  
PIC16LF1518@SSOP28(ISP) [CX0001]  
PIC16LF1518@UQFN28(ISP) [CX0001]  
PIC16LF1519(ISP) [CX0001]  
PIC16LF1519@TQFP44(ISP) [CX0001]  
PIC16LF1519@UQFN40(ISP) [CX0001]  
PIC16LF1526@QFN64(ISP) [CX0001]  
PIC16LF1526@TQFP64(ISP) [CX0001]  
PIC16LF1527@QFN64(ISP) [CX0001]  
PIC16LF1527@TQFP64(ISP) [CX0001]  
PIC16LF1782(ISP) [CX0001]  
PIC16LF1782@SOIC28(ISP) [CX0001]



PIC16LF1782@SSOP28 [CX1026]                    PIC16LF1782@SSOP28(ISP) [CX0001]  
PIC16LF1782@UQFN28 [CX4014]                   PIC16LF1782@UQFN28(ISP) [CX0001]  
PIC16LF1783 [CX0001]                           PIC16LF1783(ISP) [CX0001]  
PIC16LF1783@SOIC28 [CX1033]                   PIC16LF1783@SOIC28(ISP) [CX0001]  
PIC16LF1783@SSOP28 [CX1026]                   PIC16LF1783@SSOP28(ISP) [CX0001]  
PIC16LF1783@UQFN28 [CX4014]                   PIC16LF1783@UQFN28(ISP) [CX0001]  
PIC16LF1784 [CX0001]                           PIC16LF1784(ISP) [CX0001]  
PIC16LF1784@QFN44 [CX4019]                   PIC16LF1784@TQFP44 [CX3003]  
PIC16LF1784@UQFN40                           PIC16LF1786 [CX0001]  
PIC16LF1786(ISP) [CX0001]                   PIC16LF1786@QFN28 [CX4014]  
PIC16LF1786@SOIC28 [CX1033]                   PIC16LF1786@SSOP28 [CX1026]  
PIC16LF1787 [CX0001]                           PIC16LF1787(ISP) [CX0001]  
PIC16LF1787@QFN44 [CX4019]                   PIC16LF1787@TQFP44 [CX3003]  
PIC16LF1787@UQFN40                           PIC16LF1788 [CX0001]  
PIC16LF1788(ISP) [CX0001]                   PIC16LF1788@QFN28 [CX4014]  
PIC16LF1788@SOIC28 [CX1033]                   PIC16LF1788@SSOP28 [CX1026]  
PIC16LF1789 [CX0001]                           PIC16LF1789(ISP) [CX0001]  
PIC16LF1789@QFN44 [CX4019]                   PIC16LF1789@TQFP44 [CX3003]  
PIC16LF1789@UQFN40                           PIC16LF1823 [CX0001]  
PIC16LF1823(8-word) [CX0001]                   PIC16LF1823(ISP)(HV) [CX0001]  
PIC16LF1823(LV) [CX0001]                      PIC16LF1823(LVISP) [CX0001]  
PIC16LF1823@QFN16(3\*3) [CX4008]  
PIC16LF1823@QFN16(3\*3)(8-word) [CX4008]  
PIC16LF1823@QFN16(3\*3)(ISP)(HV) [CX0001]  
PIC16LF1823@QFN16(3\*3)(LV) [CX4008]  
PIC16LF1823@QFN16(4\*4) [CX4010]  
PIC16LF1823@QFN16(4\*4)(8-word) [CX4010]  
PIC16LF1823@QFN16(4\*4)(ISP)(HV) [CX0001]  
PIC16LF1823@QFN16(4\*4)(LV) [CX4010]  
PIC16LF1823@SOIC14 [CX1016]  
PIC16LF1823@SOIC14(8-word) [CX1016]  
PIC16LF1823@SOIC14(ISP)(HV) [CX0001]  
PIC16LF1823@SOIC14(LV) [CX1016]              PIC16LF1823@TSSOP14 [CX1000]  
PIC16LF1823@TSSOP14(8-word) [CX1000]  
PIC16LF1823@TSSOP14(ISP)(HV) [CX0001]  
PIC16LF1823@TSSOP14(LV) [CX1000]            PIC16LF1824 [CX0001]  
PIC16LF1824(8-word) [CX0001]                   PIC16LF1824(ISP)(HV) [CX0001]  
PIC16LF1824(LV) [CX0001]                      PIC16LF1824(LVISP) [CX0001]  
PIC16LF1824@QFN16(3\*3) [CX4008]  
PIC16LF1824@QFN16(3\*3)(8-word) [CX4008]  
PIC16LF1824@QFN16(3\*3)(ISP)(HV) [CX0001]  
PIC16LF1824@QFN16(3\*3)(LV) [CX4008]  
PIC16LF1824@QFN16(4\*4) [CX4010]  
PIC16LF1824@QFN16(4\*4)(8-word) [CX4010]  
PIC16LF1824@QFN16(4\*4)(ISP)(HV) [CX0001]  
PIC16LF1824@QFN16(4\*4)(LV) [CX4010]  
PIC16LF1824@SOIC14 [CX1016]  
PIC16LF1824@SOIC14(8-word) [CX1016]  
PIC16LF1824@SOIC14(ISP)(HV) [CX0001]  
PIC16LF1824@SOIC14(LV) [CX1016]              PIC16LF1824@TSSOP14 [CX1000]  
PIC16LF1824@TSSOP14(8-word) [CX1000]  
PIC16LF1824@TSSOP14(ISP)(HV) [CX0001]  
PIC16LF1824@TSSOP14(LV) [CX1000]            PIC16LF1825 [CX0001]  
PIC16LF1825(8-word) [CX0001]                   PIC16LF1825(ISP)(HV) [CX0001]  
PIC16LF1825(LV) [CX0001]                      PIC16LF1825(LVISP) [CX0001]  
PIC16LF1825@QFN16(3\*3) [CX4008]  
PIC16LF1825@QFN16(3\*3)(8-word) [CX4008]  
PIC16LF1825@QFN16(3\*3)(ISP)(HV) [CX0001]  
PIC16LF1825@QFN16(3\*3)(LV) [CX4008]

PIC16LF1825@QFN16(4\*4) [CX4010]  
PIC16LF1825@QFN16(4\*4)(8-word) [CX4010]  
PIC16LF1825@QFN16(4\*4)(ISP)(HV) [CX0001]  
PIC16LF1825@QFN16(4\*4)(LV) [CX4010]  
PIC16LF1825@SOIC14 [CX1016]  
PIC16LF1825@SOIC14(8-word) [CX1016]  
PIC16LF1825@SOIC14(ISP)(HV) [CX0001]  
PIC16LF1825@SOIC14(LV) [CX1016] PIC16LF1825@TSSOP14 [CX1000]  
PIC16LF1825@TSSOP14(8-word) [CX1000]  
PIC16LF1825@TSSOP14(ISP)(HV) [CX0001]  
PIC16LF1825@TSSOP14(LV) [CX1000] PIC16LF1826 [CX0001]  
PIC16LF1826(8-word) [CX0001] PIC16LF1826(ISP)(HV) [CX0001]  
PIC16LF1826(LV) [CX0001] PIC16LF1826(LVISP) [CX0001]  
PIC16LF1826@QFN28 [CX4014]  
PIC16LF1826@QFN28(8-word) [CX4014]  
PIC16LF1826@QFN28(ISP)(HV) [CX0001]  
PIC16LF1826@QFN28(LV) [CX4014] PIC16LF1826@SOIC18 [CX1033]  
PIC16LF1826@SOIC18(8-word) [CX1033]  
PIC16LF1826@SOIC18(ISP)(HV) [CX0001]  
PIC16LF1826@SOIC18(LV) [CX1033] PIC16LF1826@SSOP20 [CX1070]  
PIC16LF1826@SSOP20(8-word) [CX1070]  
PIC16LF1826@SSOP20(ISP)(HV) [CX0001]  
PIC16LF1826@SSOP20(LV) [CX1026] PIC16LF1827 [CX0001]  
PIC16LF1827(8-word) [CX0001] PIC16LF1827(ISP)(HV) [CX0001]  
PIC16LF1827(LV) [CX0001] PIC16LF1827(LVISP) [CX0001]  
PIC16LF1827@QFN28 [CX4014]  
PIC16LF1827@QFN28(8-word) [CX4014]  
PIC16LF1827@QFN28(ISP)(HV) [CX0001]  
PIC16LF1827@QFN28(LV) [CX4014] PIC16LF1827@SOIC18 [CX1033]  
PIC16LF1827@SOIC18(8-word) [CX1033]  
PIC16LF1827@SOIC18(ISP)(HV) [CX0001]  
PIC16LF1827@SOIC18(LV) [CX1033] PIC16LF1827@SSOP20 [CX1070]  
PIC16LF1827@SSOP20(8-word) [CX1070]  
PIC16LF1827@SSOP20(ISP)(HV) [CX0001]  
PIC16LF1827@SSOP20(LV) [CX1026] PIC16LF1828 [CX0001]  
PIC16LF1828(8-word) [CX0001] PIC16LF1828(ISP)(HV) [CX0001]  
PIC16LF1828(LV) [CX0001] PIC16LF1828(LVISP) [CX0001]  
PIC16LF1828@QFN20 [CX4011]  
PIC16LF1828@QFN20(8-word) [CX4011]  
PIC16LF1828@QFN20(ISP)(HV) [CX0001]  
PIC16LF1828@QFN20(LV) [CX4011] PIC16LF1828@SOIC20 [CX1033]  
PIC16LF1828@SOIC20(8-word) [CX1033]  
PIC16LF1828@SOIC20(ISP)(HV) [CX0001]  
PIC16LF1828@SOIC20(LV) [CX1033] PIC16LF1828@TSSOP20 [CX1070]  
PIC16LF1828@TSSOP20(8-word) [CX1070]  
PIC16LF1828@TSSOP20(ISP)(HV) [CX0001]  
PIC16LF1828@TSSOP20(LV) [CX1026] PIC16LF1829 [CX0001]  
PIC16LF1829(8-word) [CX0001] PIC16LF1829(ISP)(HV) [CX0001]  
PIC16LF1829(LV) [CX0001] PIC16LF1829(LVISP) [CX0001]  
PIC16LF1829@QFN20 [CX4011]  
PIC16LF1829@QFN20(8-word) [CX4011]  
PIC16LF1829@QFN20(ISP)(HV) [CX0001]  
PIC16LF1829@QFN20(LV) [CX4011] PIC16LF1829@SOIC20 [CX1033]  
PIC16LF1829@SOIC20(8-word) [CX1033]  
PIC16LF1829@SOIC20(ISP)(HV) [CX0001]  
PIC16LF1829@SOIC20(LV) [CX1033] PIC16LF1829@TSSOP20 [CX1070]  
PIC16LF1829@TSSOP20(8-word) [CX1070]  
PIC16LF1829@TSSOP20(ISP)(HV) [CX0001]  
PIC16LF1829@TSSOP20(LV) [CX1026] PIC16LF1847 [CX0001]

PIC16LF1847(ISP)(HV) [CX0001] PIC16LF1847@QFN28 [CX4014]  
PIC16LF1847@QFN28(ISP)(HV) [CX0001]  
PIC16LF1847@SOIC18 [CX1033]  
PIC16LF1847@SOIC18(ISP)(HV) [CX0001]  
PIC16LF1847@SSOP20 [CX1026]  
PIC16LF1847@SSOP20(ISP)(HV) [CX0001]  
PIC16LF1847E [CX0001] PIC16LF1847E@QFN28 [CX4014]  
PIC16LF1847E@SOIC18 [CX1033] PIC16LF1847E@SSOP20 [CX1026]  
PIC16LF1902 [CX0001] PIC16LF1902(ISP)(HV) [CX0001]  
PIC16LF1902@QFN28 [CX4014]  
PIC16LF1902@QFN28(ISP)(HV) [CX0001]  
PIC16LF1902@QFN28[8-word pro] [CX4014]  
PIC16LF1902@SOIC28 [CX1033]  
PIC16LF1902@SOIC28(ISP)(HV) [CX0001]  
PIC16LF1902@SOIC28[8-word pro] [CX1033]  
PIC16LF1902@SSOP28 [CX1026]  
PIC16LF1902@SSOP28(ISP)(HV) [CX0001]  
PIC16LF1902@SSOP28[8-word pro] [CX1026]  
PIC16LF1902[8-word pro] [CX0001] PIC16LF1903 [CX0001]  
PIC16LF1903(ISP)(HV) [CX0001] PIC16LF1903@QFN28 [CX4014]  
PIC16LF1903@QFN28(ISP)(HV) [CX0001]  
PIC16LF1903@QFN28[8-word pro] [CX4014]  
PIC16LF1903@SOIC28 [CX1033]  
PIC16LF1903@SOIC28(ISP)(HV) [CX0001]  
PIC16LF1903@SOIC28[8-word pro] [CX1033]  
PIC16LF1903@SSOP28 [CX1026]  
PIC16LF1903@SSOP28(ISP)(HV) [CX0001]  
PIC16LF1903@SSOP28[8-word pro] [CX1026]  
PIC16LF1903[8-word pro] [CX0001] PIC16LF1904 [CX0001]  
PIC16LF1904(ISP)(HV) [CX0001] PIC16LF1904@TQFP44 [CX3003]  
PIC16LF1904@TQFP44(ISP)(HV) [CX0001]  
PIC16LF1904@TQFP44[8-word pro] [CX3003]  
PIC16LF1904@UQFN40 [CX4039]  
PIC16LF1904@UQFN40(ISP)(HV) [CX0001]  
PIC16LF1904@UQFN40[8-word pro] [CX4039]  
PIC16LF1904[8-word pro] [CX0001] PIC16LF1906 [CX0001]  
PIC16LF1906(ISP)(HV) [CX0001] PIC16LF1906@QFN28 [CX4014]  
PIC16LF1906@QFN28(ISP)(HV) [CX0001]  
PIC16LF1906@QFN28[8-word pro] [CX4014]  
PIC16LF1906@SOIC28 [CX1033]  
PIC16LF1906@SOIC28(ISP)(HV) [CX0001]  
PIC16LF1906@SOIC28[8-word pro] [CX1033]  
PIC16LF1906@SSOP28 [CX1026]  
PIC16LF1906@SSOP28(ISP)(HV) [CX0001]  
PIC16LF1906@SSOP28[8-word pro] [CX1026]  
PIC16LF1906[8-word pro] [CX0001] PIC16LF1907 [CX0001]  
PIC16LF1907(ISP)(HV) [CX0001] PIC16LF1907@TQFP44 [CX3003]  
PIC16LF1907@TQFP44(ISP)(HV) [CX0001]  
PIC16LF1907@TQFP44[8-word pro] [CX3003]  
PIC16LF1907@UQFN40 [CX4039]  
PIC16LF1907@UQFN40(ISP)(HV) [CX0001]  
PIC16LF1907@UQFN40[8-word pro] [CX4039]  
PIC16LF1907[8-word pro] [CX0001] PIC16LF1933 [CX0001]  
PIC16LF1933(ISP)(HV) [CX0001] PIC16LF1933@QFN28 [CX4014]  
PIC16LF1933@QFN28(ISP)(HV) [CX0001]  
PIC16LF1933@QFN28[8-word pro] [CX4014]  
PIC16LF1933@SOIC28 [CX1033]  
PIC16LF1933@SOIC28(ISP)(HV) [CX0001]  
PIC16LF1933@SOIC28[8-word pro] [CX1033]

PIC16LF1933@SSOP28 [CX1026]  
PIC16LF1933@SSOP28(ISP)(HV) [CX0001]  
PIC16LF1933@SSOP28[8-word pro] [CX1026]  
PIC16LF1933@UQFN28 [CX4036] PIC16LF1933[8-word pro] [CX0001]  
PIC16LF1934 [CX0001] PIC16LF1934(ISP)(HV) [CX0001]  
PIC16LF1934@QFN44 [CX4019]  
PIC16LF1934@QFN44(ISP)(HV) [CX0001]  
PIC16LF1934@QFN44[8-word pro] [CX4019]  
PIC16LF1934@TQFP44 [CX3003]  
PIC16LF1934@TQFP44(ISP)(HV) [CX0001]  
PIC16LF1934@TQFP44[8-word pro] [CX3003]  
PIC16LF1934[8-word pro] [CX0001] PIC16LF1936 [CX0001]  
PIC16LF1936(ISP)(HV) [CX0001] PIC16LF1936@QFN28 [CX4014]  
PIC16LF1936@QFN28(ISP)(HV) [CX0001]  
PIC16LF1936@QFN28[8-word pro] [CX4014]  
PIC16LF1936@SOIC28 [CX1033]  
PIC16LF1936@SOIC28(ISP)(HV) [CX0001]  
PIC16LF1936@SOIC28[8-word pro] [CX1033]  
PIC16LF1936@SSOP28 [CX1026]  
PIC16LF1936@SSOP28(ISP)(HV) [CX0001]  
PIC16LF1936@SSOP28[8-word pro] [CX1026]  
PIC16LF1936@UQFN28 [CX4036] PIC16LF1936[8-word pro] [CX0001]  
PIC16LF1937 [CX0001] PIC16LF1937(ISP)(HV) [CX0001]  
PIC16LF1937@QFN44 [CX4019]  
PIC16LF1937@QFN44(ISP)(HV) [CX0001]  
PIC16LF1937@QFN44[8-word pro] [CX4019]  
PIC16LF1937@TQFP44 [CX3003]  
PIC16LF1937@TQFP44(ISP)(HV) [CX0001]  
PIC16LF1937@TQFP44[8-word pro] [CX3003]  
PIC16LF1937[8-word pro] [CX0001] PIC16LF1938 [CX0001]  
PIC16LF1938(ISP)(HV) [CX0001] PIC16LF1938@QFN28 [CX4014]  
PIC16LF1938@QFN28(ISP)(HV) [CX0001]  
PIC16LF1938@QFN28[8-word pro] [CX4014]  
PIC16LF1938@SOIC28 [CX1033]  
PIC16LF1938@SOIC28(ISP)(HV) [CX0001]  
PIC16LF1938@SOIC28[8-word pro] [CX1033]  
PIC16LF1938@SSOP28 [CX1026]  
PIC16LF1938@SSOP28(ISP)(HV) [CX0001]  
PIC16LF1938@SSOP28[8-word pro] [CX1026]  
PIC16LF1938@UQFN28 [CX4036] PIC16LF1938[8-word pro] [CX0001]  
PIC16LF1939 [CX0001] PIC16LF1939(ISP)(HV) [CX0001]  
PIC16LF1939@QFN44 [CX4019]  
PIC16LF1939@QFN44(ISP)(HV) [CX0001]  
PIC16LF1939@QFN44[8-word pro] [CX4019]  
PIC16LF1939@TQFP44 [CX3003]  
PIC16LF1939@TQFP44(ISP)(HV) [CX0001]  
PIC16LF1939@TQFP44[8-word pro] [CX3003]  
PIC16LF1939[8-word pro] [CX0001] PIC16LF1946@QFN64 [CX4023]  
PIC16LF1946@QFN64(ISP)(HV) [CX0001]  
PIC16LF1946@QFN64[8-word pro] [CX4023]  
PIC16LF1946@TQFP64 [CX3011]  
PIC16LF1946@TQFP64(ISP)(HV) [CX0001]  
PIC16LF1946@TQFP64[8-word pro] [CX3011]  
PIC16LF1947@QFN64 [CX4023]  
PIC16LF1947@QFN64(ISP)(HV) [CX0001]  
PIC16LF1947@QFN64[8-word pro] [CX4023]  
PIC16LF1947@TQFP64 [CX3011]  
PIC16LF1947@TQFP64(ISP)(HV) [CX0001]  
PIC16LF1947@TQFP64[8-word pro] [CX3011]

PIC16LF505 [CX0001]  
PIC16LF505@SOIC14 [CX1065]  
PIC16LF505@TSSOP14 [CX1000]  
PIC16LF506 [CX0001]  
PIC16LF506@SOIC14 [CX1030]  
PIC16LF506@TSSOP14 [CX1001]  
PIC16LF526 [CX0001]  
PIC16LF526@SOIC14 [CX1016]  
PIC16LF526@TSSOP14 [CX1000]  
PIC16LF54 [CX0001]  
PIC16LF54@SOIC18 [CX1033]  
PIC16LF54@SSOP20 [CX1026]  
PIC16LF57 [CX0001]  
PIC16LF57@SOIC28 [CX1033]  
PIC16LF57@SSOP28 [CX1026]  
PIC16LF59 [CX0001]  
PIC16LF59@PLCC44 [CX2044]  
PIC16LF59@TQFP44 [CX3003]  
PIC16LF627 [CX0001]  
PIC16LF627@SOIC18 [CX1033]  
PIC16LF627@SSOP20 [CX1026]  
PIC16LF627A [CX0001]  
PIC16LF627A@SOIC18 [CX1033]  
PIC16LF627A@SSOP20 [CX1026]  
PIC16LF628 [CX0001]  
PIC16LF628@SOIC18 [CX1033]  
PIC16LF628@SSOP20 [CX1026]  
PIC16LF628A [CX0001]  
PIC16LF628A@SOIC18 [CX1033]  
PIC16LF628A@SSOP20 [CX1026]  
PIC16LF631 [CX0001]  
PIC16LF631@QFN20 [CX4011]  
PIC16LF631@SOIC20 [CX1033]  
PIC16LF631@SSOP20 [CX1070]  
PIC16LF639 [CX0001]  
PIC16LF639@QFN20 [CX4011]  
PIC16LF639@SOIC20 [CX1033]  
PIC16LF639@SSOP20 [CX1070]  
PIC16LF648A [CX0001]  
PIC16LF648A@SOIC18 [CX1033]  
PIC16LF648A@SSOP20 [CX1026]  
PIC16LF677 [CX0001]  
PIC16LF677@QFN20 [CX4011]  
PIC16LF677@SOIC20 [CX1033]  
PIC16LF677@SSOP20 [CX1070]  
PIC16LF685 [CX0001]  
PIC16LF685@QFN20 [CX4011]  
PIC16LF685@SOIC20 [CX1033]  
PIC16LF685@SSOP20 [CX1070]  
PIC16LF687 [CX0001]  
PIC16LF687@QFN20 [CX4011]  
PIC16LF687@SOIC20 [CX1033]  
PIC16LF687@SSOP20 [CX1070]  
PIC16LF689 [CX0001]  
PIC16LF689@QFN20 [CX4011]  
PIC16LF689@SOIC20 [CX1033]  
PIC16LF689@SSOP20 [CX1070]  
PIC16LF690 [CX0001]  
PIC16LF690@QFN20 [CX4011]

PIC16LF505(ISP) [CX0001]  
PIC16LF505@SOIC14(ISP) [CX0001]  
PIC16LF505@TSSOP14(ISP) [CX0001]  
PIC16LF506(ISP) [CX0001]  
PIC16LF506@SOIC14(ISP) [CX0001]  
PIC16LF506@TSSOP14(ISP) [CX0001]  
PIC16LF526(ISP) [CX0001]  
PIC16LF526@SOIC14(ISP) [CX0001]  
PIC16LF526@TSSOP14(ISP) [CX0001]  
PIC16LF54(ISP) [CX0001]  
PIC16LF54@SOIC18(ISP) [CX0001]  
PIC16LF54@SSOP20(ISP) [CX0001]  
PIC16LF57(ISP) [CX0001]  
PIC16LF57@SOIC28(ISP) [CX0001]  
PIC16LF57@SSOP28(ISP) [CX0001]  
PIC16LF59(ISP) [CX0001]  
PIC16LF59@PLCC44(ISP) [CX0001]  
PIC16LF59@TQFP44(ISP) [CX0001]  
PIC16LF627(ISP) [CX0001]  
PIC16LF627@SOIC18(ISP) [CX0001]  
PIC16LF627@SSOP20(ISP) [CX0001]  
PIC16LF627A(ISP) [CX0001]  
PIC16LF627A@SOIC18(ISP) [CX0001]  
PIC16LF627A@SSOP20(ISP) [CX0001]  
PIC16LF628(ISP) [CX0001]  
PIC16LF628@SOIC18(ISP) [CX0001]  
PIC16LF628@SSOP20(ISP) [CX0001]  
PIC16LF628A(ISP) [CX0001]  
PIC16LF628A@SOIC18(ISP) [CX0001]  
PIC16LF628A@SSOP20(ISP) [CX0001]  
PIC16LF631(ISP) [CX0001]  
PIC16LF631@QFN20(ISP) [CX0001]  
PIC16LF631@SOIC20(ISP) [CX0001]  
PIC16LF631@SSOP20(ISP) [CX0001]  
PIC16LF639(ISP) [CX0001]  
PIC16LF639@QFN20(ISP) [CX0001]  
PIC16LF639@SOIC20(ISP) [CX0001]  
PIC16LF639@SSOP20(ISP) [CX0001]  
PIC16LF648A(ISP) [CX0001]  
PIC16LF648A@SOIC18(ISP) [CX0001]  
PIC16LF648A@SSOP20(ISP) [CX0001]  
PIC16LF677(ISP) [CX0001]  
PIC16LF677@QFN20(ISP) [CX0001]  
PIC16LF677@SOIC20(ISP) [CX0001]  
PIC16LF677@SSOP20(ISP) [CX0001]  
PIC16LF685(ISP) [CX0001]  
PIC16LF685@QFN20(ISP) [CX0001]  
PIC16LF685@SOIC20(ISP) [CX0001]  
PIC16LF685@SSOP20(ISP) [CX0001]  
PIC16LF687(ISP) [CX0001]  
PIC16LF687@QFN20(ISP) [CX0001]  
PIC16LF687@SOIC20(ISP) [CX0001]  
PIC16LF687@SSOP20(ISP) [CX0001]  
PIC16LF689(ISP) [CX0001]  
PIC16LF689@QFN20(ISP) [CX0001]  
PIC16LF689@SOIC20(ISP) [CX0001]  
PIC16LF689@SSOP20(ISP) [CX0001]  
PIC16LF690(ISP) [CX0001]  
PIC16LF690@QFN20(ISP) [CX0001]

PIC16LF690@SOIC20 [CX1033]                    PIC16LF690@SOIC20(ISP) [CX0001]  
PIC16LF690@SSOP20 [CX1070]                    PIC16LF690@SSOP20(ISP) [CX0001]  
PIC16LF707 [CX0001]                            PIC16LF707(ISP) [CX0001]  
PIC16LF707@QFN44 [CX4019]                    PIC16LF707@QFN44(ISP) [CX0001]  
PIC16LF707@TQFP44 [CX3003]                   PIC16LF707@TQFP44(ISP) [CX0001]  
PIC16LF716 [CX0001]                            PIC16LF716(4-WORD PRO) [CX0001]  
PIC16LF716(ISP) [CX0001]                    PIC16LF716@SOIC18 [CX1033]  
PIC16LF716@SOIC18(4-WORD PRO) [CX1033]  
PIC16LF716@SOIC18(ISP) [CX0001]            PIC16LF716@SSOP20 [CX1026]  
PIC16LF716@SSOP20(4-WORD PRO) [CX1026]  
PIC16LF716@SSOP20(ISP) [CX0001]            PIC16LF72 [CX0001]  
PIC16LF72(ISP) [CX0001]                      PIC16LF72@QFN28 [CX4014]  
PIC16LF72@QFN28(ISP) [CX0001]              PIC16LF72@SOIC28 [CX1033]  
PIC16LF72@SOIC28(ISP) [CX0001]              PIC16LF72@SSOP28 [CX1026]  
PIC16LF72@SSOP28(ISP) [CX0001]              PIC16LF720 [CX0001]  
PIC16LF720@QFN20 [CX4011]                    PIC16LF720@SOIC20 [CX1033]  
PIC16LF720@SSOP20 [CX1026]                   PIC16LF721 [CX0001]  
PIC16LF721@QFN20 [CX4011]                    PIC16LF721@SOIC20 [CX1033]  
PIC16LF721@SSOP20 [CX1026]                   PIC16LF722 [CX0001]  
PIC16LF722(ISP) [CX0001]                    PIC16LF722@QFN28 [CX4014]  
PIC16LF722@QFN28(ISP) [CX0001]            PIC16LF722@SOIC28 [CX1033]  
PIC16LF722@SOIC28(ISP) [CX0001]            PIC16LF722@SSOP28 [CX1077]  
PIC16LF722@SSOP28(ISP) [CX0001]            PIC16LF722A [CX0001]  
PIC16LF722A(ISP) [CX0001]                    PIC16LF722A@QFN28 [CX4014]  
PIC16LF722A@QFN28(ISP) [CX0001]            PIC16LF722A@SOIC28 [CX1033]  
PIC16LF722A@SOIC28(ISP) [CX0001]            PIC16LF722A@SSOP28 [CX1077]  
PIC16LF722A@SSOP28(ISP) [CX0001]            PIC16LF723 [CX0001]  
PIC16LF723(ISP) [CX0001]                    PIC16LF723@QFN28 [CX4014]  
PIC16LF723@QFN28(ISP) [CX0001]            PIC16LF723@SOIC28 [CX1033]  
PIC16LF723@SOIC28(ISP) [CX0001]            PIC16LF723@SSOP28 [CX1077]  
PIC16LF723@SSOP28(ISP) [CX0001]            PIC16LF723A [CX0001]  
PIC16LF723A(ISP) [CX0001]                    PIC16LF723A@QFN28 [CX4014]  
PIC16LF723A@QFN28(ISP) [CX0001]            PIC16LF723A@SOIC28 [CX1033]  
PIC16LF723A@SOIC28(ISP) [CX0001]            PIC16LF723A@SSOP28 [CX1077]  
PIC16LF723A@SSOP28(ISP) [CX0001]            PIC16LF724 [CX0001]  
PIC16LF724(ISP) [CX0001]                    PIC16LF724@QFN44 [CX4019]  
PIC16LF724@QFN44(ISP) [CX0001]            PIC16LF724@TQFP44 [CX3003]  
PIC16LF724@TQFP44(ISP) [CX0001]            PIC16LF726 [CX0001]  
PIC16LF726(ISP) [CX0001]                    PIC16LF726@QFN28 [CX4014]  
PIC16LF726@QFN28(ISP) [CX0001]            PIC16LF726@SOIC28 [CX1033]  
PIC16LF726@SOIC28(ISP) [CX0001]            PIC16LF726@SSOP28 [CX1077]  
PIC16LF726@SSOP28(ISP) [CX0001]            PIC16LF727 [CX0001]  
PIC16LF727(ISP) [CX0001]                    PIC16LF727@QFN44 [CX4019]  
PIC16LF727@QFN44(ISP) [CX0001]            PIC16LF727@TQFP44 [CX3003]  
PIC16LF727@TQFP44(ISP) [CX0001]            PIC16LF73 [CX0001]  
PIC16LF73(ISP) [CX0001]                      PIC16LF73@QFN28 [CX4014]  
PIC16LF73@SOIC28 [CX1033]                    PIC16LF73@SOIC28(ISP) [CX0001]  
PIC16LF73@SSOP28 [CX1026]                    PIC16LF73@SSOP28(ISP) [CX0001]  
PIC16LF737 [CX0001]                            PIC16LF737(ISP) [CX0001]  
PIC16LF737@SOIC28 [CX1033]                    PIC16LF737@SOIC28(ISP) [CX0001]  
PIC16LF737@SSOP28 [CX1077]                   PIC16LF737@SSOP28(ISP) [CX0001]  
PIC16LF74 [CX0001]                            PIC16LF74(ISP) [CX0001]  
PIC16LF74@PLCC44 [CX2044]                    PIC16LF74@PLCC44(ISP) [CX0001]  
PIC16LF74@TQFP44 [CX3003]                    PIC16LF74@TQFP44(ISP) [CX0001]  
PIC16LF747 [CX0001]                            PIC16LF747(ISP) [CX0001]  
PIC16LF747@TQFP44 [CX3003]                    PIC16LF747@TQFP44(ISP) [CX0001]  
PIC16LF76 [CX0001]                            PIC16LF76(ISP) [CX0001]  
PIC16LF76@QFN28 [CX4014]                    PIC16LF76@SOIC28 [CX1033]  
PIC16LF76@SOIC28(ISP) [CX0001]            PIC16LF76@SSOP28 [CX1026]

PIC16LF76@SSOP28(ISP) [CX0001]      PIC16LF767 [CX0001]  
PIC16LF767(ISP) [CX0001]      PIC16LF767@SOIC28 [CX1033]  
PIC16LF767@SOIC28(ISP) [CX0001]      PIC16LF767@SSOP28 [CX1077]  
PIC16LF767@SSOP28(ISP) [CX0001]      PIC16LF77 [CX0001]  
PIC16LF77(ISP) [CX0001]      PIC16LF77@PLCC44 [CX2044]  
PIC16LF77@PLCC44(ISP) [CX0001]      PIC16LF77@TQFP44 [CX3003]  
PIC16LF77@TQFP44(ISP) [CX0001]      PIC16LF777 [CX0001]  
PIC16LF777(ISP) [CX0001]      PIC16LF777@TQFP44 [CX3003]  
PIC16LF777@TQFP44(ISP) [CX0001]      PIC16LF818 [CX0001]  
PIC16LF818(ISP) [CX0001]      PIC16LF818@QFN28 [CX4014]  
PIC16LF818@QFN28(ISP) [CX0001]      PIC16LF818@SOIC18 [CX1033]  
PIC16LF818@SOIC18(ISP) [CX0001]      PIC16LF818@SSOP20 [CX1026]  
PIC16LF818@SSOP20(ISP) [CX0001]      PIC16LF819 [CX0001]  
PIC16LF819(ISP) [CX0001]      PIC16LF819@QFN28 [CX4014]  
PIC16LF819@QFN28(ISP) [CX0001]      PIC16LF819@SOIC18 [CX1033]  
PIC16LF819@SOIC18(ISP) [CX0001]      PIC16LF819@SSOP20 [CX1026]  
PIC16LF819@SSOP20(ISP) [CX0001]      PIC16LF83 [CX0001]  
PIC16LF83(ISP) [CX0001]      PIC16LF83@SOIC18 [CX1033]  
PIC16LF83@SOIC18(ISP) [CX0001]      PIC16LF84 [CX0001]  
PIC16LF84(ISP) [CX0001]      PIC16LF84@SOIC18 [CX1033]  
PIC16LF84@SOIC18(ISP) [CX0001]      PIC16LF84A [CX0001]  
PIC16LF84A(ISP) [CX0001]      PIC16LF84A@SOIC18 [CX1033]  
PIC16LF84A@SOIC18(ISP) [CX0001]      PIC16LF84A@SSOP20 [CX1026]  
PIC16LF84A@SSOP20(ISP) [CX0001]      PIC16LF87 [CX0001]  
PIC16LF87(ISP) [CX0001]      PIC16LF87@QFN28 [CX4014]  
PIC16LF87@QFN28(ISP) [CX0001]      PIC16LF87@SOIC18 [CX1033]  
PIC16LF87@SOIC18(ISP) [CX0001]      PIC16LF87@SSOP20 [CX1026]  
PIC16LF87@SSOP20(ISP) [CX0001]      PIC16LF870 [CX0001]  
PIC16LF870(ISP)      PIC16LF870@SOIC28 [CX1033]  
PIC16LF870@SOIC28(ISP)      PIC16LF870@SSOP28 [CX1026]  
PIC16LF870@SSOP28(ISP)      PIC16LF871 [CX0001]  
PIC16LF871(ISP)      PIC16LF871@MQFP44 [CX3088]  
PIC16LF871@MQFP44(ISP)      PIC16LF871@PLCC44 [CX2044]  
PIC16LF871@PLCC44(ISP)      PIC16LF871@TQFP44 [CX3003]  
PIC16LF871@TQFP44(ISP)      PIC16LF872 [CX0001]  
PIC16LF872(ISP)      PIC16LF872@SOIC28 [CX1033]  
PIC16LF872@SOIC28(ISP)      PIC16LF872@SSOP28 [CX1026]  
PIC16LF872@SSOP28(ISP)      PIC16LF873 [CX0001]  
PIC16LF873(ISP)      PIC16LF873@SOIC28 [CX1033]  
PIC16LF873@SOIC28(ISP)      PIC16LF873A [CX0001]  
PIC16LF873A(ISP)(High-V) [CX0001]  
PIC16LF873A(ISP)(Low-V) [CX0001]  
PIC16LF873A(ISP3.3v)(HV) [CX0001]  
PIC16LF873A(ISP3.3v)(LV) [CX0001]  
PIC16LF873A@QFN28 [CX4014]  
PIC16LF873A@QFN28(ISP)(High-V) [CX0001]  
PIC16LF873A@QFN28(ISP)(Low-V) [CX0001]  
PIC16LF873A@QFN28(ISP3.3v)(HV) [CX0001]  
PIC16LF873A@QFN28(ISP3.3v)(LV) [CX0001]  
PIC16LF873A@SOIC28 [CX1033]  
PIC16LF873A@SOIC28(ISP)(High-V) [CX0001]  
PIC16LF873A@SOIC28(ISP)(Low-V) [CX0001]  
PIC16LF873A@SOIC28(ISP3.3v)(HV) [CX0001]  
PIC16LF873A@SOIC28(ISP3.3v)(LV) [CX0001]  
PIC16LF873A@SSOP28 [CX1026]  
PIC16LF873A@SSOP28(ISP)(High-V) [CX0001]  
PIC16LF873A@SSOP28(ISP)(Low-V) [CX0001]  
PIC16LF873A@SSOP28(ISP3.3v)(HV) [CX0001]  
PIC16LF873A@SSOP28(ISP3.3v)(LV) [CX0001]

PIC16LF874 [CX0001] PIC16LF874(ISP)  
PIC16LF874@MQFP44 [CX3088] PIC16LF874@MQFP44(ISP)  
PIC16LF874@PLCC44 [CX2044] PIC16LF874@PLCC44(ISP)  
PIC16LF874@TQFP44 [CX3003] PIC16LF874@TQFP44(ISP)  
PIC16LF874A [CX0001]  
PIC16LF874A(ISP)(High-V) [CX0001]  
PIC16LF874A(ISP)(Low-V) [CX0001]  
PIC16LF874A(ISP3.3v)(HV) [CX0001]  
PIC16LF874A(ISP3.3v)(LV) [CX0001]  
PIC16LF874A@PLCC44 [CX2044]  
PIC16LF874A@PLCC44(ISP)(High-V) [CX0001]  
PIC16LF874A@PLCC44(ISP)(Low-V) [CX0001]  
PIC16LF874A@PLCC44(ISP3.3v)(HV) [CX0001]  
PIC16LF874A@PLCC44(ISP3.3v)(LV) [CX0001]  
PIC16LF874A@TQFP44 [CX3003]  
PIC16LF874A@TQFP44(ISP)(High-V) [CX0001]  
PIC16LF874A@TQFP44(ISP)(Low-V) [CX0001]  
PIC16LF874A@TQFP44(ISP3.3v)(HV) [CX0001]  
PIC16LF874A@TQFP44(ISP3.3v)(LV) [CX0001]  
PIC16LF876 [CX0001] PIC16LF876(ISP)  
PIC16LF876@SOIC28 [CX1033] PIC16LF876@SOIC28(ISP)  
PIC16LF876A [CX0001]  
PIC16LF876A(ISP)(High-V) [CX0001]  
PIC16LF876A(ISP)(Low-V) [CX0001]  
PIC16LF876A(ISP3.3v)(HV) [CX0001]  
PIC16LF876A(ISP3.3v)(LV) [CX0001]  
PIC16LF876A@QFN28 [CX4014]  
PIC16LF876A@QFN28(ISP)(High-V) [CX0001]  
PIC16LF876A@QFN28(ISP)(Low-V) [CX0001]  
PIC16LF876A@QFN28(ISP3.3v)(HV) [CX0001]  
PIC16LF876A@QFN28(ISP3.3v)(LV) [CX0001]  
PIC16LF876A@SOIC28 [CX1033]  
PIC16LF876A@SOIC28(ISP)(High-V) [CX0001]  
PIC16LF876A@SOIC28(ISP)(Low-V) [CX0001]  
PIC16LF876A@SOIC28(ISP3.3v)(HV) [CX0001]  
PIC16LF876A@SOIC28(ISP3.3v)(LV) [CX0001]  
PIC16LF876A@SSOP28 [CX1026]  
PIC16LF876A@SSOP28(ISP)(High-V) [CX0001]  
PIC16LF876A@SSOP28(ISP)(Low-V) [CX0001]  
PIC16LF876A@SSOP28(ISP3.3v)(HV) [CX0001]  
PIC16LF876A@SSOP28(ISP3.3v)(LV) [CX0001]  
PIC16LF877 [CX0001] PIC16LF877(ISP)  
PIC16LF877@MQFP44 [CX3088] PIC16LF877@MQFP44(ISP)  
PIC16LF877@PLCC44 [CX2044] PIC16LF877@PLCC44(ISP)  
PIC16LF877@TQFP44 [CX3003] PIC16LF877@TQFP44(ISP)  
PIC16LF877A [CX0001]  
PIC16LF877A(ISP)(High-V) [CX0001]  
PIC16LF877A(ISP)(Low-V) [CX0001]  
PIC16LF877A(ISP3.3v)(HV) [CX0001]  
PIC16LF877A(ISP3.3v)(LV) [CX0001]  
PIC16LF877A@PLCC44 [CX2044]  
PIC16LF877A@PLCC44(ISP)(High-V) [CX0001]  
PIC16LF877A@PLCC44(ISP)(Low-V) [CX0001]  
PIC16LF877A@PLCC44(ISP3.3v)(HV) [CX0001]  
PIC16LF877A@PLCC44(ISP3.3v)(LV) [CX0001]  
PIC16LF877A@TQFP44 [CX3003]  
PIC16LF877A@TQFP44(ISP)(High-V) [CX0001]  
PIC16LF877A@TQFP44(ISP)(Low-V) [CX0001]  
PIC16LF877A@TQFP44(ISP3.3v)(HV) [CX0001]



PIC16LF877A@TQFP44(ISP3.3v)(LV) [CX0001]  
PIC16LF88 [CX0001] PIC16LF88(ISP) [CX0001]  
PIC16LF88@QFN28 [CX4014] PIC16LF88@QFN28(ISP) [CX0001]  
PIC16LF88@SOIC18 [CX1033] PIC16LF88@SOIC18(ISP) [CX0001]  
PIC16LF88@SSOP20 [CX1026] PIC16LF88@SSOP20(ISP) [CX0001]  
PIC16LF913 [CX0001] PIC16LF913(ISP) [CX0001]  
PIC16LF913@QFN28 [CX4014] PIC16LF913@QFN28(ISP) [CX0001]  
PIC16LF913@SOIC28 [CX1033] PIC16LF913@SOIC28(ISP) [CX0001]  
PIC16LF913@SSOP28 [CX1026] PIC16LF913@SSOP28(ISP) [CX0001]  
PIC16LF914 [CX0001] PIC16LF914(ISP) [CX0001]  
PIC16LF914@QFN44 [CX4018] PIC16LF914@QFN44(ISP) [CX0001]  
PIC16LF914@QFN44(ML) [CX4019]  
PIC16LF914@QFN44(ML)(ISP) [CX0001]  
PIC16LF914@TQFP44 [CX3003] PIC16LF914@TQFP44(ISP) [CX0001]  
PIC16LF916 [CX0001] PIC16LF916(ISP) [CX0001]  
PIC16LF916@QFN28 [CX4014] PIC16LF916@QFN28(ISP) [CX0001]  
PIC16LF916@SOIC28 [CX1033] PIC16LF916@SOIC28(ISP) [CX0001]  
PIC16LF916@SSOP28 [CX1026] PIC16LF916@SSOP28(ISP) [CX0001]  
PIC16LF917 [CX0001] PIC16LF917(ISP) [CX0001]  
PIC16LF917@QFN44 [CX4018] PIC16LF917@QFN44(ISP) [CX0001]  
PIC16LF917@QFN44(ML) [CX4019]  
PIC16LF917@QFN44(ML)(ISP) [CX0001]  
PIC16LF917@TQFP44 [CX3003] PIC16LF917@TQFP44(ISP) [CX0001]  
PIC16LF946@TQFP64 [CX3011] PIC16LF946@TQFP64(ISP) [CX0001]  
PIC16LV54A [CX0001] PIC16LV54A@SOIC18 [CX1033]  
PIC16LV54A@SSOP20 [CX1026] PIC16LV58A [CX0001]  
PIC16LV58A@SOIC18 [CX1033] PIC16LV58A@SSOP20 [CX1026]  
PIC17C42 [CX0001] PIC17C42@PLCC44 [CX2044]  
PIC17C42@TQFP44 [CX3003] PIC17C42A [CX0001]  
PIC17C42A@PLCC44 [CX2044] PIC17C42A@TQFP44 [CX3003]  
PIC17C43 [CX0001] PIC17C43@PLCC44 [CX2044]  
PIC17C43@TQFP44 [CX3003] PIC17C44 [CX0001]  
PIC17C44@PLCC44 [CX2044] PIC17C44@TQFP44 [CX3003]  
PIC17LC42 [CX0001] PIC17LC42@PLCC44 [CX2044]  
PIC17LC42@TQFP44 [CX3003] PIC17LC42A [CX0001]  
PIC17LC42A@PLCC44 [CX2044] PIC17LC42A@TQFP44 [CX3003]  
PIC17LC43 [CX0001] PIC17LC43@PLCC44 [CX2044]  
PIC17LC43@TQFP44 [CX3003] PIC17LC44 [CX0001]  
PIC17LC44@PLCC44 [CX2044] PIC17LC44@TQFP44 [CX3003]  
PIC18C242 [CX0001] PIC18C242@SOIC28 [CX1033]  
PIC18C252 [CX0001] PIC18C252@SOIC28 [CX1033]  
PIC18C442 [CX0001] PIC18C442@PLCC44 [CX2044]  
PIC18C442@TQFP44 [CX3003] PIC18C452 [CX0001]  
PIC18C452@PLCC44 [CX2044] PIC18C452@TQFP44 [CX3003]  
PIC18C658@PLCC68 [CX2068] PIC18C658@TQFP64 [CX3011]  
PIC18C858@PLCC84 [CX2084] PIC18C858@TQFP80 [CX3016]  
PIC18F1220 [CX0001] PIC18F1220(ISP) [CX0001]  
PIC18F1220@QFN28 [CX4014] PIC18F1220@SOIC18 [CX1033]  
PIC18F1220@SOIC18(ISP) [CX0001] PIC18F1220@SSOP20 [CX1026]  
PIC18F1220@SSOP20(ISP) [CX0001] PIC18F1230 [CX0001]  
PIC18F1230(ISP) [CX0001] PIC18F1230@QFN28 [CX4014]  
PIC18F1230@QFN28(ISP) [CX0001] PIC18F1230@SOIC18 [CX1033]  
PIC18F1230@SOIC18(ISP) [CX0001] PIC18F1230@SSOP20 [CX1026]  
PIC18F1230@SSOP20(ISP) [CX0001] PIC18F1320 [CX0001]  
PIC18F1320(ISP) [CX0001] PIC18F1320@QFN28 [CX4014]  
PIC18F1320@SOIC18 [CX1033] PIC18F1320@SOIC18(ISP) [CX0001]  
PIC18F1320@SSOP20 [CX1026] PIC18F1320@SSOP20(ISP) [CX0001]  
PIC18F1330 [CX0001] PIC18F1330(ISP) [CX0001]  
PIC18F1330@QFN28 [CX4014] PIC18F1330@QFN28(ISP) [CX0001]

PIC18F1330@SOIC18 [CX1033] PIC18F1330@SOIC18(ISP) [CX0001]  
PIC18F1330@SSOP20 [CX1026] PIC18F1330@SSOP20(ISP) [CX0001]  
PIC18F1330-ICD@QFN28 [CX4014]  
PIC18F1330-ICD@QFN28(ISP) [CX0001]  
PIC18F13K22 [CX0001]  
PIC18F13K22(ISP)(High-V) [CX0001]  
PIC18F13K22(ISP)(Low-V) [CX0001] PIC18F13K22@QFN20 [CX4011]  
PIC18F13K22@QFN20(ISP)(High-V) [CX0001]  
PIC18F13K22@QFN20(ISP)(Low-V) [CX0001]  
PIC18F13K22@SOIC20 [CX1033]  
PIC18F13K22@SOIC20(ISP)(High-V) [CX0001]  
PIC18F13K22@SOIC20(ISP)(Low-V) [CX0001]  
PIC18F13K22@SSOP20 [CX1026]  
PIC18F13K22@SSOP20(ISP)(High-V) [CX0001]  
PIC18F13K22@SSOP20(ISP)(Low-V) [CX0001]  
PIC18F13K50 [CX0001]  
PIC18F13K50(ISP)(High-V) [CX0001]  
PIC18F13K50(ISP)(Low-V) [CX0001] PIC18F13K50@QFN20 [CX4025]  
PIC18F13K50@QFN20(ISP)(High-V) [CX0001]  
PIC18F13K50@QFN20(ISP)(Low-V) [CX0001]  
PIC18F13K50@SOIC20 [CX1033]  
PIC18F13K50@SOIC20(ISP)(High-V) [CX0001]  
PIC18F13K50@SOIC20(ISP)(Low-V) [CX0001]  
PIC18F13K50@SSOP20 [CX1026]  
PIC18F13K50@SSOP20(ISP)(High-V) [CX0001]  
PIC18F13K50@SSOP20(ISP)(Low-V) [CX0001]  
PIC18F14K22 [CX0001]  
PIC18F14K22(ISP)(High-V) [CX0001]  
PIC18F14K22(ISP)(Low-V) [CX0001] PIC18F14K22@QFN20 [CX4011]  
PIC18F14K22@QFN20(ISP)(High-V) [CX0001]  
PIC18F14K22@QFN20(ISP)(Low-V) [CX0001]  
PIC18F14K22@SOIC20 [CX1033]  
PIC18F14K22@SOIC20(ISP)(High-V) [CX0001]  
PIC18F14K22@SOIC20(ISP)(Low-V) [CX0001]  
PIC18F14K22@SSOP20 [CX1026]  
PIC18F14K22@SSOP20(ISP)(High-V) [CX0001]  
PIC18F14K22@SSOP20(ISP)(Low-V) [CX0001]  
PIC18F14K50 [CX0001]  
PIC18F14K50(ISP)(High-V) [CX0001]  
PIC18F14K50(ISP)(Low-V) [CX0001] PIC18F14K50@QFN20 [CX4025]  
PIC18F14K50@QFN20(ISP)(High-V) [CX0001]  
PIC18F14K50@QFN20(ISP)(Low-V) [CX0001]  
PIC18F14K50@SOIC20 [CX1033]  
PIC18F14K50@SOIC20(ISP)(High-V) [CX0001]  
PIC18F14K50@SOIC20(ISP)(Low-V) [CX0001]  
PIC18F14K50@SSOP20 [CX1026]  
PIC18F14K50@SSOP20(ISP)(High-V) [CX0001]  
PIC18F14K50@SSOP20(ISP)(Low-V) [CX0001]  
PIC18F2220 [CX0001] PIC18F2220(ISP) [CX0001]  
PIC18F2220@SOIC28 [CX1033] PIC18F2220@SOIC28(ISP) [CX0001]  
PIC18F2221 [CX0001] PIC18F2221(ISP)(Low-V) [CX0001]  
PIC18F2221@QFN28 [CX4014]  
PIC18F2221@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2221@SOIC28 [CX1033]  
PIC18F2221@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2221@SSOP28 [CX1026]  
PIC18F2221@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2320 [CX0001] PIC18F2320(ISP) [CX0001]  
PIC18F2320@SOIC28 [CX1033] PIC18F2320@SOIC28(ISP) [CX0001]

PIC18F2321 [CX0001] PIC18F2321(ISP)(Low-V) [CX0001]  
PIC18F2321@QFN28 [CX4014]  
PIC18F2321@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2321@SOIC28 [CX1033]  
PIC18F2321@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2321@SSOP28 [CX1026]  
PIC18F2321@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2331 [CX0001] PIC18F2331(ISP) [CX0001]  
PIC18F2331@SOIC28 [CX1033] PIC18F2331@SOIC28(ISP) [CX0001]  
PIC18F23K20 [CX0001]  
PIC18F23K20(ISP)(High-V) [CX0001]  
PIC18F23K20(ISP)(Low-V) [CX0001] PIC18F23K20@QFN28 [CX4014]  
PIC18F23K20@QFN28(ISP)(High-V) [CX0001]  
PIC18F23K20@QFN28(ISP)(Low-V) [CX0001]  
PIC18F23K20@SOIC28 [CX1033]  
PIC18F23K20@SOIC28(ISP)(High-V) [CX0001]  
PIC18F23K20@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F23K20@SSOP28 [CX1026]  
PIC18F23K20@SSOP28(ISP)(High-V) [CX0001]  
PIC18F23K20@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F23K20@UQFN28 [CX4036] PIC18F23K22 [CX0001]  
PIC18F23K22(ISP)(H-V) [CX0001] PIC18F23K22@QFN28 [CX4014]  
PIC18F23K22@QFN28(ISP)(H-V) [CX0001]  
PIC18F23K22@SOIC28 [CX1033]  
PIC18F23K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18F23K22@SSOP28 [CX1026]  
PIC18F23K22@SSOP28(ISP)(H-V) [CX0001]  
PIC18F23K22@UQFN28 [CX4036] PIC18F2410 [CX0001]  
PIC18F2410(ISP)(Low-V) [CX0001] PIC18F2410@QFN28 [CX4014]  
PIC18F2410@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2410@SOIC28 [CX1033]  
PIC18F2410@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2410@SSOP28 [CX1026]  
PIC18F2410@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F242 [CX0001] PIC18F242(ISP) [CX0001]  
PIC18F242@SOIC28 [CX1033] PIC18F242@SOIC28(ISP) [CX0001]  
PIC18F2420 [CX0001] PIC18F2420(ISP)(High-V) [CX0001]  
PIC18F2420(ISP)(Low-V) [CX0001] PIC18F2420@QFN28 [CX4014]  
PIC18F2420@QFN28(ISP)(High-V) [CX0001]  
PIC18F2420@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2420@SOIC28 [CX1033]  
PIC18F2420@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2420@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2420@SSOP28 [CX1026]  
PIC18F2420@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2420@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2423 [CX0001] PIC18F2423(ISP)(High-V) [CX0001]  
PIC18F2423(ISP)(Low-V) [CX0001] PIC18F2423@QFN28 [CX4014]  
PIC18F2423@QFN28(ISP)(High-V) [CX0001]  
PIC18F2423@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2423@SOIC28 [CX1033]  
PIC18F2423@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2423@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2423@SSOP28 [CX1026]  
PIC18F2423@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2423@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2431 [CX0001] PIC18F2431(ISP) [CX0001]  
PIC18F2431@SOIC28 [CX1033] PIC18F2431@SOIC28(ISP) [CX0001]  
PIC18F2439 [CX0001] PIC18F2439(ISP) [CX0001]

PIC18F2439@SOIC28 [CX1033] PIC18F2439@SOIC28(ISP) [CX0001]  
PIC18F2450 [CX0001] PIC18F2450(ISP)(Low-V) [CX0001]  
PIC18F2450@QFN28 [CX4014]  
PIC18F2450@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2450@SOIC28 [CX1033]  
PIC18F2450@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2450@SSOP28 [CX1026]  
PIC18F2450@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2455 [CX0001] PIC18F2455(ISP)(High-V) [CX0001]  
PIC18F2455(ISP)(Low-V) [CX0001] PIC18F2455@SOIC28 [CX1033]  
PIC18F2455@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2455@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2455@SSOP28 [CX1026]  
PIC18F2455@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2455@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2458 [CX0001] PIC18F2458(ISP)(High-V) [CX0001]  
PIC18F2458(ISP)(Low-V) [CX0001] PIC18F2458@SOIC28 [CX1033]  
PIC18F2458@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2458@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2458@SSOP28  
PIC18F2458@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2458@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F248 [CX0001] PIC18F248(ISP) [CX0001]  
PIC18F248@SOIC28 [CX1033] PIC18F248@SOIC28(ISP) [CX0001]  
PIC18F2480 [CX0001] PIC18F2480(ISP)(High-V) [CX0001]  
PIC18F2480(ISP)(Low-V) [CX0001] PIC18F2480@QFN28 [CX4014]  
PIC18F2480@QFN28(ISP)(High-V) [CX0001]  
PIC18F2480@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2480@SOIC28 [CX1033]  
PIC18F2480@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2480@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2480@SSOP28 [CX1026]  
PIC18F2480@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2480@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F24J10 [CX0001] PIC18F24J10(ISP) [CX0001]  
PIC18F24J10@QFN28 [CX4014] PIC18F24J10@QFN28(ISP) [CX0001]  
PIC18F24J10@SOIC28 [CX1033] PIC18F24J10@SOIC28(ISP) [CX0001]  
PIC18F24J10@SSOP28 [CX1026] PIC18F24J10@SSOP28(ISP) [CX0001]  
PIC18F24J11 [CX0001] PIC18F24J11(ISP) [CX0001]  
PIC18F24J11@QFN28 [CX4014] PIC18F24J11@QFN28(ISP) [CX0001]  
PIC18F24J11@SOIC28 [CX1033] PIC18F24J11@SOIC28(ISP) [CX0001]  
PIC18F24J11@SSOP28 [CX1026] PIC18F24J11@SSOP28(ISP) [CX0001]  
PIC18F24J50 [CX0001] PIC18F24J50(ISP) [CX0001]  
PIC18F24J50@QFN28 [CX4014] PIC18F24J50@QFN28(ISP) [CX0001]  
PIC18F24J50@SOIC28 [CX1033] PIC18F24J50@SOIC28(ISP) [CX0001]  
PIC18F24J50@SSOP28 [CX1026] PIC18F24J50@SSOP28(ISP) [CX0001]  
PIC18F24K20 [CX0001]  
PIC18F24K20(ISP)(High-V) [CX0001]  
PIC18F24K20(ISP)(Low-V) [CX0001] PIC18F24K20@QFN28 [CX4014]  
PIC18F24K20@QFN28(ISP)(High-V) [CX0001]  
PIC18F24K20@QFN28(ISP)(Low-V) [CX0001]  
PIC18F24K20@SOIC28 [CX1033]  
PIC18F24K20@SOIC28(ISP)(High-V) [CX0001]  
PIC18F24K20@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F24K20@SSOP28 [CX1026]  
PIC18F24K20@SSOP28(ISP)(High-V) [CX0001]  
PIC18F24K20@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F24K20@UQFN28 [CX4036] PIC18F24K22 [CX0001]  
PIC18F24K22(ISP)(H-V) [CX0001] PIC18F24K22@QFN28 [CX4014]

PIC18F24K22@QFN28(ISP)(H-V) [CX0001]  
PIC18F24K22@SOIC28 [CX1033]  
PIC18F24K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18F24K22@SSOP28 [CX1026]  
PIC18F24K22@SSOP28(ISP)(H-V) [CX0001]  
PIC18F24K22@UQFN28 [CX4036] PIC18F24K50 [CX0001]  
PIC18F24K50@ISP [CX0001] PIC18F24K50@QFN28 [CX4014]  
PIC18F24K50@SOIC28 [CX1033] PIC18F24K50@SSOP28 [CX1026]  
PIC18F2510 [CX0001] PIC18F2510(ISP) [CX0001]  
PIC18F2510@QFN28 [CX4014] PIC18F2510@QFN28(ISP) [CX0001]  
PIC18F2510@SOIC28 [CX1033] PIC18F2510@SOIC28(ISP) [CX0001]  
PIC18F2510@SSOP28 [CX1026] PIC18F2510@SSOP28(ISP) [CX0001]  
PIC18F2515 [CX0001] PIC18F2515(ISP)(Low-V) [CX0001]  
PIC18F2515@SOIC28 [CX1033]  
PIC18F2515@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2515@SSOP28 [CX1026]  
PIC18F2515@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F252 [CX0001] PIC18F252(ISP) [CX0001]  
PIC18F252@SOIC28 [CX1033] PIC18F252@SOIC28(ISP) [CX0001]  
PIC18F2520 [CX0001] PIC18F2520(ISP)(High-V) [CX0001]  
PIC18F2520(ISP)(Low-V) [CX0001] PIC18F2520@QFN28 [CX4014]  
PIC18F2520@QFN28(ISP)(High-V) [CX0001]  
PIC18F2520@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2520@SOIC28 [CX1033]  
PIC18F2520@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2520@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2520@SSOP28 [CX1026]  
PIC18F2520@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2520@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2523 [CX0001] PIC18F2523(ISP)(High-V) [CX0001]  
PIC18F2523(ISP)(Low-V) [CX0001] PIC18F2523@QFN28 [CX4014]  
PIC18F2523@QFN28(ISP)(High-V) [CX0001]  
PIC18F2523@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2523@SOIC28 [CX1033]  
PIC18F2523@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2523@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2523@SSOP28 [CX1026]  
PIC18F2523@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2523@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2525 [CX0001] PIC18F2525(ISP)(Low-V) [CX0001]  
PIC18F2525@SOIC28 [CX1033]  
PIC18F2525@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2525@SSOP28 [CX1026]  
PIC18F2525@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2539 [CX0001] PIC18F2539(ISP) [CX0001]  
PIC18F2539@SOIC28 [CX1033] PIC18F2539@SOIC28(ISP) [CX0001]  
PIC18F2550 [CX0001] PIC18F2550(ISP)(High-V) [CX0001]  
PIC18F2550(ISP)(Low-V) [CX0001] PIC18F2550@SOIC28 [CX1033]  
PIC18F2550@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2550@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2550@SSOP28 [CX1026]  
PIC18F2550@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2550@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2553 [CX0001] PIC18F2553(ISP)(High-V) [CX0001]  
PIC18F2553(ISP)(Low-V) [CX0001] PIC18F2553@SOIC28 [CX1033]  
PIC18F2553@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2553@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2553@SSOP28  
PIC18F2553@SSOP28(ISP)(High-V) [CX0001]

PIC18F2553@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F258 [CX0001] PIC18F258(ISP) [CX0001]  
PIC18F258@SOIC28 [CX1033] PIC18F258@SOIC28(ISP) [CX0001]  
PIC18F2580 [CX0001] PIC18F2580(ISP)(High-V) [CX0001]  
PIC18F2580(ISP)(Low-V) [CX0001] PIC18F2580@QFN28 [CX4014]  
PIC18F2580@QFN28(ISP)(High-V) [CX0001]  
PIC18F2580@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2580@SOIC28 [CX1033]  
PIC18F2580@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2580@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2580@SSOP28 [CX1026]  
PIC18F2580@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2580@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2585 [CX0001] PIC18F2585(ISP)(High-V) [CX0001]  
PIC18F2585(ISP)(Low-V) [CX0001] PIC18F2585@SDIP28 [CX0032]  
PIC18F2585@SDIP28(ISP)(High-V) [CX0001]  
PIC18F2585@SDIP28(ISP)(Low-V) [CX0001]  
PIC18F2585@SOIC28 [CX1033]  
PIC18F2585@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2585@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2585@SSOP28 [CX1026]  
PIC18F2585@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2585@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F25J10 [CX0001] PIC18F25J10(ISP) [CX0001]  
PIC18F25J10@QFN28 [CX4014] PIC18F25J10@QFN28(ISP) [CX0001]  
PIC18F25J10@SOIC28 [CX1033] PIC18F25J10@SOIC28(ISP) [CX0001]  
PIC18F25J10@SSOP28 [CX1026] PIC18F25J10@SSOP28(ISP) [CX0001]  
PIC18F25J11 [CX0001] PIC18F25J11(ISP) [CX0001]  
PIC18F25J11@QFN28 [CX4014] PIC18F25J11@QFN28(ISP) [CX0001]  
PIC18F25J11@SOIC28 [CX1033] PIC18F25J11@SOIC28(ISP) [CX0001]  
PIC18F25J11@SSOP28 [CX1026] PIC18F25J11@SSOP28(ISP) [CX0001]  
PIC18F25J50 [CX0001] PIC18F25J50(ISP) [CX0001]  
PIC18F25J50@QFN28 [CX4014] PIC18F25J50@QFN28(ISP) [CX0001]  
PIC18F25J50@SOIC28 [CX1033] PIC18F25J50@SOIC28(ISP) [CX0001]  
PIC18F25J50@SSOP28 [CX1026] PIC18F25J50@SSOP28(ISP) [CX0001]  
PIC18F25K20 [CX0001]  
PIC18F25K20(ISP)(High-V) [CX0001]  
PIC18F25K20(ISP)(Low-V) [CX0001] PIC18F25K20@QFN28 [CX4014]  
PIC18F25K20@QFN28(ISP)(High-V) [CX0001]  
PIC18F25K20@QFN28(ISP)(Low-V) [CX0001]  
PIC18F25K20@SOIC28 [CX1033]  
PIC18F25K20@SOIC28(ISP)(High-V) [CX0001]  
PIC18F25K20@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F25K20@SSOP28 [CX1026]  
PIC18F25K20@SSOP28(ISP)(High-V) [CX0001]  
PIC18F25K20@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F25K20@UQFN28 [CX4036] PIC18F25K22 [CX0001]  
PIC18F25K22(ISP)(H-V) [CX0001] PIC18F25K22@QFN28 [CX4014]  
PIC18F25K22@QFN28(ISP)(H-V) [CX0001]  
PIC18F25K22@SOIC28 [CX1033]  
PIC18F25K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18F25K22@SSOP28 [CX1026]  
PIC18F25K22@SSOP28(ISP)(H-V) [CX0001]  
PIC18F25K22@UQFN28 [CX4036] PIC18F25K50 [CX0001]  
PIC18F25K50@ISP [CX0001] PIC18F25K50@QFN28 [CX4014]  
PIC18F25K50@SOIC28 [CX1033] PIC18F25K50@SSOP28 [CX1026]  
PIC18F25K80 [CX0001] PIC18F25K80(ISP) [CX0001]  
PIC18F25K80@QFN28 [CX4014] PIC18F25K80@QFN28(ISP) [CX0001]  
PIC18F25K80@SOIC28 [CX1033] PIC18F25K80@SOIC28(ISP) [CX0001]

PIC18F25K80@SSOP28 [CX1026] PIC18F25K80@SSOP28(ISP) [CX0001]  
PIC18F25LK80@QFN28(ISP) [CX0001] PIC18F2610 [CX0001]  
PIC18F2610(ISP)(Low-V) [CX0001] PIC18F2610@SOIC28 [CX1033]  
PIC18F2610@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2610@SSOP28 [CX1026]  
PIC18F2610@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2620 [CX0001] PIC18F2620(ISP)(Low-V) [CX0001]  
PIC18F2620@SOIC28 [CX1033]  
PIC18F2620@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2620@SSOP28 [CX1026]  
PIC18F2620@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2680 [CX0001] PIC18F2680(ISP)(High-V) [CX0001]  
PIC18F2680(ISP)(Low-V) [CX0001] PIC18F2680@SDIP28 [CX0032]  
PIC18F2680@SDIP28(ISP)(High-V) [CX0001]  
PIC18F2680@SDIP28(ISP)(Low-V) [CX0001]  
PIC18F2680@SOIC28 [CX1033]  
PIC18F2680@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2680@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2680@SSOP28 [CX1026]  
PIC18F2680@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2680@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2682 [CX0001] PIC18F2682(ISP)(High-V) [CX0001]  
PIC18F2682(ISP)(Low-V) [CX0001] PIC18F2682@QFN28 [CX4014]  
PIC18F2682@QFN28(ISP)(High-V) [CX0001]  
PIC18F2682@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2682@SOIC28 [CX1033]  
PIC18F2682@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2682@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2682@SSOP28 [CX1026]  
PIC18F2682@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2682@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F2685 [CX0001] PIC18F2685(ISP)(High-V) [CX0001]  
PIC18F2685(ISP)(Low-V) [CX0001] PIC18F2685@QFN28 [CX4014]  
PIC18F2685@QFN28(ISP)(High-V) [CX0001]  
PIC18F2685@QFN28(ISP)(Low-V) [CX0001]  
PIC18F2685@SOIC28 [CX1033]  
PIC18F2685@SOIC28(ISP)(High-V) [CX0001]  
PIC18F2685@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F2685@SSOP28 [CX1026]  
PIC18F2685@SSOP28(ISP)(High-V) [CX0001]  
PIC18F2685@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F26J11 [CX0001] PIC18F26J11(ISP) [CX0001]  
PIC18F26J11@QFN28 [CX4014] PIC18F26J11@QFN28(ISP) [CX0001]  
PIC18F26J11@SOIC28 [CX1033] PIC18F26J11@SOIC28(ISP) [CX0001]  
PIC18F26J11@SSOP28 [CX1026] PIC18F26J11@SSOP28(ISP) [CX0001]  
PIC18F26J13 [CX0001] PIC18F26J13(ISP) [CX0001]  
PIC18F26J13@QFN28 [CX4014] PIC18F26J13@QFN28(ISP) [CX0001]  
PIC18F26J13@SOIC28 [CX1033] PIC18F26J13@SOIC28(ISP) [CX0001]  
PIC18F26J13@SSOP28 [CX1026] PIC18F26J13@SSOP28(ISP) [CX0001]  
PIC18F26J50 [CX0001] PIC18F26J50(ISP) [CX0001]  
PIC18F26J50@QFN28 [CX4014] PIC18F26J50@QFN28(ISP) [CX0001]  
PIC18F26J50@SOIC28 [CX1033] PIC18F26J50@SOIC28(ISP) [CX0001]  
PIC18F26J50@SSOP28 [CX1026] PIC18F26J50@SSOP28(ISP) [CX0001]  
PIC18F26J53 [CX0001] PIC18F26J53(ISP) [CX0001]  
PIC18F26J53@QFN28 [CX4014] PIC18F26J53@QFN28(ISP) [CX0001]  
PIC18F26J53@SOIC28 [CX1033] PIC18F26J53@SOIC28(ISP) [CX0001]  
PIC18F26J53@SSOP28 [CX1026] PIC18F26J53@SSOP28(ISP) [CX0001]  
PIC18F26K20 [CX0001]  
PIC18F26K20(ISP)(High-V) [CX0001]

PIC18F26K20(ISP)(Low-V) [CX0001] PIC18F26K20@QFN28 [CX4014]  
PIC18F26K20@QFN28(ISP)(High-V) [CX0001]  
PIC18F26K20@QFN28(ISP)(Low-V) [CX0001]  
PIC18F26K20@SOIC28 [CX1033]  
PIC18F26K20@SOIC28(ISP)(High-V) [CX0001]  
PIC18F26K20@SOIC28(ISP)(Low-V) [CX0001]  
PIC18F26K20@SSOP28 [CX1026]  
PIC18F26K20@SSOP28(ISP)(High-V) [CX0001]  
PIC18F26K20@SSOP28(ISP)(Low-V) [CX0001]  
PIC18F26K20@UQFN28 [CX4036] PIC18F26K22 [CX0001]  
PIC18F26K22(ISP)(H-V) [CX0001] PIC18F26K22@QFN28 [CX4014]  
PIC18F26K22@QFN28(ISP)(H-V) [CX0001]  
PIC18F26K22@SOIC28 [CX1033]  
PIC18F26K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18F26K22@SSOP28 [CX1026]  
PIC18F26K22@SSOP28(ISP)(H-V) [CX0001]  
PIC18F26K22@UQFN28 [CX4036] PIC18F26K50 [CX0001]  
PIC18F26K50@ISP [CX0001] PIC18F26K50@QFN28 [CX4014]  
PIC18F26K50@SOIC28 [CX1033] PIC18F26K50@SSOP28 [CX1026]  
PIC18F26K80 [CX0001] PIC18F26K80(ISP) [CX0001]  
PIC18F26K80@QFN28 [CX4014] PIC18F26K80@QFN28(ISP) [CX0001]  
PIC18F26K80@SOIC28 [CX1033] PIC18F26K80@SOIC28(ISP) [CX0001]  
PIC18F26K80@SSOP28 [CX1026] PIC18F26K80@SSOP28(ISP) [CX0001]  
PIC18F27J13 [CX0001] PIC18F27J13(ISP) [CX0001]  
PIC18F27J13@QFN28 [CX4014] PIC18F27J13@QFN28(ISP) [CX0001]  
PIC18F27J13@SOIC28 [CX1033] PIC18F27J13@SOIC28(ISP) [CX0001]  
PIC18F27J13@SSOP28 [CX1026] PIC18F27J13@SSOP28(ISP) [CX0001]  
PIC18F27J53 [CX0001] PIC18F27J53(ISP) [CX0001]  
PIC18F27J53@QFN28 [CX4014] PIC18F27J53@QFN28(ISP) [CX0001]  
PIC18F27J53@SOIC28 [CX1033] PIC18F27J53@SOIC28(ISP) [CX0001]  
PIC18F27J53@SSOP28 [CX1026] PIC18F27J53@SSOP28(ISP) [CX0001]  
PIC18F4220 [CX0001] PIC18F4220(ISP) [CX0001]  
PIC18F4220@QFN44 [CX4018] PIC18F4220@QFN44(ISP) [CX0001]  
PIC18F4220@QFN44(ML) [CX4019]  
PIC18F4220@QFN44(ML)(ISP) [CX0001]  
PIC18F4220@TQFP44 [CX3003] PIC18F4220@TQFP44(ISP) [CX0001]  
PIC18F4221 [CX0001] PIC18F4221(ISP)(Low-V) [CX0001]  
PIC18F4221@QFN44 [CX4018]  
PIC18F4221@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4221@QFN44(ML) [CX4019]  
PIC18F4221@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4221@TQFP44 [CX3003]  
PIC18F4221@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4320 [CX0001] PIC18F4320(ISP) [CX0001]  
PIC18F4320@QFN44 [CX4018] PIC18F4320@QFN44(ISP) [CX0001]  
PIC18F4320@QFN44(ML) [CX4019]  
PIC18F4320@QFN44(ML)(ISP) [CX0001]  
PIC18F4320@TQFP44 [CX3003] PIC18F4320@TQFP44(ISP) [CX0001]  
PIC18F4321 [CX0001] PIC18F4321(ISP)(Low-V) [CX0001]  
PIC18F4321@QFN44 [CX4018]  
PIC18F4321@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4321@QFN44(ML) [CX4019]  
PIC18F4321@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4321@TQFP44 [CX3003]  
PIC18F4321@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4331 [CX0001] PIC18F4331(ISP) [CX0001]  
PIC18F4331@TQFP44 [CX3003] PIC18F4331@TQFP44(ISP) [CX0001]  
PIC18F43K20 [CX0001]  
PIC18F43K20(ISP)(High-V) [CX0001]



PIC18F43K20(ISP)(Low-V) [CX0001] PIC18F43K20@QFN44 [CX4018]  
PIC18F43K20@QFN44(ISP)(High-V) [CX0001]  
PIC18F43K20@QFN44(ISP)(Low-V) [CX0001]  
PIC18F43K20@QFN44(ML) [CX4019]  
PIC18F43K20@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F43K20@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18F43K20@TQFP44 [CX3003]  
PIC18F43K20@TQFP44(ISP)(High-V) [CX0001]  
PIC18F43K20@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F43K20@UQFN40 [CX4039] PIC18F43K22 [CX0001]  
PIC18F43K22(ISP)(H-V) [CX0001] PIC18F43K22@QFN44 [CX4018]  
PIC18F43K22@QFN44(ISP)(H-V) [CX0001]  
PIC18F43K22@QFN44(ML) [CX4019]  
PIC18F43K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F43K22@TQFP44 [CX3003]  
PIC18F43K22@TQFP44(ISP)(H-V) [CX0001]  
PIC18F43K22@UQFN40 [CX4039] PIC18F4410 [CX0001]  
PIC18F4410(ISP)(Low-V) [CX0001] PIC18F4410@QFN44 [CX4018]  
PIC18F4410@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4410@QFN44(ML) [CX4019]  
PIC18F4410@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4410@TQFP44 [CX3003]  
PIC18F4410@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F442 [CX0001] PIC18F442(ISP) [CX0001]  
PIC18F442@PLCC44 [CX2044] PIC18F442@PLCC44(ISP) [CX0001]  
PIC18F442@QFN44 [CX4019] PIC18F442@TQFP44 [CX3003]  
PIC18F442@TQFP44(ISP) [CX0001] PIC18F4420 [CX0001]  
PIC18F4420(ISP)(Low-V) [CX0001] PIC18F4420@QFN44 [CX4018]  
PIC18F4420@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4420@QFN44(ML) [CX4019]  
PIC18F4420@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4420@TQFP44 [CX3003]  
PIC18F4420@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4423 [CX0001] PIC18F4423(ISP)(High-V) [CX0001]  
PIC18F4423(ISP)(Low-V) [CX0001] PIC18F4423@QFN44 [CX4018]  
PIC18F4423@QFN44(ISP)(High-V) [CX0001]  
PIC18F4423@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4423@QFN44(ML) [CX4019]  
PIC18F4423@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4423@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4423@TQFP44 [CX3003]  
PIC18F4423@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4423@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4431 [CX0001] PIC18F4431(ISP) [CX0001]  
PIC18F4431@TQFP44 [CX3003] PIC18F4431@TQFP44(ISP) [CX0001]  
PIC18F4439 [CX0001] PIC18F4439(ISP) [CX0001]  
PIC18F4439@TQFP44 [CX3003] PIC18F4439@TQFP44(ISP) [CX0001]  
PIC18F4450 [CX0001] PIC18F4450(ISP)(Low-V) [CX0001]  
PIC18F4450@QFN44 [CX4018]  
PIC18F4450@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4450@QFN44(ML) [CX4019]  
PIC18F4450@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4450@TQFP44 [CX3003]  
PIC18F4450@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4455 [CX0001] PIC18F4455(ISP)(High-V) [CX0001]  
PIC18F4455(ISP)(Low-V) [CX0001] PIC18F4455@QFN44 [CX4018]  
PIC18F4455@QFN44(ISP)(High-V) [CX0001]  
PIC18F4455@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4455@QFN44(ML) [CX4019]

PIC18F4455@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4455@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4455@TQFP44 [CX3003]  
PIC18F4455@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4455@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4458 [CX0001] PIC18F4458(ISP)(High-V) [CX0001]  
PIC18F4458(ISP)(Low-V) [CX0001] PIC18F4458@QFN44 [CX4018]  
PIC18F4458@QFN44(ISP)(High-V) [CX0001]  
PIC18F4458@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4458@TQFP44 [CX3003]  
PIC18F4458@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4458@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F448 [CX0001] PIC18F448(ISP) [CX0001]  
PIC18F448@PLCC44 [CX2044] PIC18F448@PLCC44(ISP) [CX0001]  
PIC18F448@QFN44 [CX4019] PIC18F448@TQFP44 [CX3003]  
PIC18F448@TQFP44(ISP) [CX0001] PIC18F4480 [CX0001]  
PIC18F4480(ISP)(High-V) [CX0001] PIC18F4480(ISP)(Low-V) [CX0001]  
PIC18F4480@QFN44 [CX4018]  
PIC18F4480@QFN44(ISP)(High-V) [CX0001]  
PIC18F4480@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4480@QFN44(ML) [CX4019]  
PIC18F4480@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4480@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4480@TQFP44 [CX3003]  
PIC18F4480@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4480@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F444J10 [CX0001] PIC18F444J10(ISP) [CX0001]  
PIC18F444J10@QFN44 [CX4018] PIC18F444J10@QFN44(ISP) [CX0001]  
PIC18F444J10@QFN44(ML) [CX4019]  
PIC18F444J10@QFN44(ML)(ISP) [CX0001]  
PIC18F444J10@TQFP44 [CX3003] PIC18F444J10@TQFP44(ISP) [CX0001]  
PIC18F444J11 [CX0001] PIC18F444J11(ISP) [CX0001]  
PIC18F444J11@QFN44 [CX4018] PIC18F444J11@QFN44(ISP) [CX0001]  
PIC18F444J11@QFN44(ML) [CX4019]  
PIC18F444J11@QFN44(ML)(ISP) [CX0001]  
PIC18F444J11@TQFP44 [CX3003] PIC18F444J11@TQFP44(ISP) [CX0001]  
PIC18F444J50 [CX0001] PIC18F444J50(ISP) [CX0001]  
PIC18F444J50@QFN44 [CX4018] PIC18F444J50@QFN44(ISP) [CX0001]  
PIC18F444J50@QFN44(ML) [CX4019]  
PIC18F444J50@QFN44(ML)(ISP) [CX0001]  
PIC18F444J50@TQFP44 [CX3003] PIC18F444J50@TQFP44(ISP) [CX0001]  
PIC18F44K20 [CX0001]  
PIC18F44K20(ISP)(High-V) [CX0001]  
PIC18F44K20(ISP)(Low-V) [CX0001] PIC18F44K20@QFN44 [CX4018]  
PIC18F44K20@QFN44(ISP)(High-V) [CX0001]  
PIC18F44K20@QFN44(ISP)(Low-V) [CX0001]  
PIC18F44K20@QFN44(ML) [CX4019]  
PIC18F44K20@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F44K20@QFN44(ML)(ISP)(L-V) [CX4018]  
PIC18F44K20@TQFP44 [CX3003]  
PIC18F44K20@TQFP44(ISP)(High-V) [CX0001]  
PIC18F44K20@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F44K20@UQFN40 [CX4039] PIC18F44K22 [CX0001]  
PIC18F44K22(ISP)(H-V) [CX0001] PIC18F44K22@QFN44 [CX4018]  
PIC18F44K22@QFN44(ISP)(H-V) [CX0001]  
PIC18F44K22@QFN44(ML) [CX4019]  
PIC18F44K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F44K22@TQFP44 [CX3003]  
PIC18F44K22@TQFP44(ISP)(H-V) [CX0001]

PIC18F44K22@UQFN40 [CX4039] PIC18F4510 [CX0001]  
PIC18F4510(ISP) [CX0001] PIC18F4510@QFN44 [CX4018]  
PIC18F4510@QFN44(ISP) [CX0001] PIC18F4510@QFN44(ML) [CX4019]  
PIC18F4510@QFN44(ML)(ISP) [CX0001]  
PIC18F4510@TQFP44 [CX3003] PIC18F4510@TQFP44(ISP) [CX0001]  
PIC18F4515 [CX0001] PIC18F4515(ISP)(Low-V) [CX0001]  
PIC18F4515@QFN44 [CX4018]  
PIC18F4515@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4515@QFN44(ML) [CX4019]  
PIC18F4515@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4515@TQFP44 [CX3003]  
PIC18F4515@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F452 [CX0001] PIC18F452(ISP) [CX0001]  
PIC18F452@PLCC44 [CX2044] PIC18F452@PLCC44(ISP) [CX0001]  
PIC18F452@QFN44 [CX4019] PIC18F452@TQFP44 [CX3003]  
PIC18F452@TQFP44(ISP) [CX0001] PIC18F4520 [CX0001]  
PIC18F4520(ISP) [CX0001] PIC18F4520@QFN44 [CX4018]  
PIC18F4520@QFN44(ISP) [CX0001] PIC18F4520@QFN44(ML) [CX4019]  
PIC18F4520@QFN44(ML)(ISP) [CX0001]  
PIC18F4520@TQFP44 [CX3003] PIC18F4520@TQFP44(ISP) [CX0001]  
PIC18F4523 [CX0001] PIC18F4523(ISP)(High-V) [CX0001]  
PIC18F4523(ISP)(Low-V) [CX0001] PIC18F4523@QFN44 [CX4018]  
PIC18F4523@QFN44(ISP)(High-V) [CX0001]  
PIC18F4523@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4523@QFN44(ML) [CX4019]  
PIC18F4523@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4523@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4523@TQFP44 [CX3003]  
PIC18F4523@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4523@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4525 [CX0001] PIC18F4525(ISP)(Low-V) [CX0001]  
PIC18F4525@QFN44 [CX4018]  
PIC18F4525@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4525@QFN44(ML) [CX4019]  
PIC18F4525@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4525@TQFP44 [CX3003]  
PIC18F4525@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4539 [CX0001] PIC18F4539(ISP) [CX0001]  
PIC18F4539@TQFP44 [CX3003] PIC18F4539@TQFP44(ISP) [CX0001]  
PIC18F4550 [CX0001] PIC18F4550(ISP)(High-V) [CX0001]  
PIC18F4550(ISP)(Low-V) [CX0001] PIC18F4550@QFN44 [CX4018]  
PIC18F4550@QFN44(ISP)(High-V) [CX0001]  
PIC18F4550@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4550@QFN44(ML) [CX4019]  
PIC18F4550@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4550@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4550@TQFP44 [CX3003]  
PIC18F4550@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4550@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4553 [CX0001] PIC18F4553(ISP)(High-V) [CX0001]  
PIC18F4553(ISP)(Low-V) [CX0001] PIC18F4553@QFN44 [CX4018]  
PIC18F4553@QFN44(ISP)(High-V) [CX0001]  
PIC18F4553@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4553@TQFP44 [CX3003]  
PIC18F4553@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4553@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F458 [CX0001] PIC18F458(ISP) [CX0001]  
PIC18F458@PLCC44 [CX2044] PIC18F458@PLCC44(ISP) [CX0001]  
PIC18F458@QFN44 [CX4019] PIC18F458@TQFP44 [CX3003]

PIC18F458@TQFP44(ISP) [CX0001] PIC18F4580 [CX0001]  
PIC18F4580(ISP)(High-V) [CX0001] PIC18F4580(ISP)(Low-V) [CX0001]  
PIC18F4580@QFN44 [CX4018]  
PIC18F4580@QFN44(ISP)(High-V) [CX0001]  
PIC18F4580@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4580@QFN44(ML) [CX4019]  
PIC18F4580@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4580@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4580@TQFP44 [CX3003]  
PIC18F4580@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4580@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4585 [CX0001] PIC18F4585(ISP)(High-V) [CX0001]  
PIC18F4585(ISP)(Low-V) [CX0001] PIC18F4585@QFN44 [CX4018]  
PIC18F4585@QFN44(ISP)(High-V) [CX0001]  
PIC18F4585@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4585@QFN44(ML) [CX4019]  
PIC18F4585@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4585@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4585@TQFP44 [CX3003]  
PIC18F4585@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4585@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F45J10 [CX0001] PIC18F45J10(ISP) [CX0001]  
PIC18F45J10@QFN44 [CX4018] PIC18F45J10@QFN44(ISP) [CX0001]  
PIC18F45J10@QFN44(ML) [CX4019]  
PIC18F45J10@QFN44(ML)(ISP) [CX0001]  
PIC18F45J10@TQFP44 [CX3003] PIC18F45J10@TQFP44(ISP) [CX0001]  
PIC18F45J11 [CX0001] PIC18F45J11(ISP) [CX0001]  
PIC18F45J11@QFN44 [CX4018] PIC18F45J11@QFN44(ISP) [CX0001]  
PIC18F45J11@QFN44(ML) [CX4019]  
PIC18F45J11@QFN44(ML)(ISP) [CX0001]  
PIC18F45J11@TQFP44 [CX3003] PIC18F45J11@TQFP44(ISP) [CX0001]  
PIC18F45J50 [CX0001] PIC18F45J50(ISP) [CX0001]  
PIC18F45J50@QFN44 [CX4018] PIC18F45J50@QFN44(ISP) [CX0001]  
PIC18F45J50@QFN44(ML) [CX4019]  
PIC18F45J50@QFN44(ML)(ISP) [CX0001]  
PIC18F45J50@TQFP44 [CX3003] PIC18F45J50@TQFP44(ISP) [CX0001]  
PIC18F45K20 [CX0001]  
PIC18F45K20(ISP)(High-V) [CX0001]  
PIC18F45K20(ISP)(Low-V) [CX0001] PIC18F45K20@QFN44 [CX4018]  
PIC18F45K20@QFN44(ISP)(High-V) [CX0001]  
PIC18F45K20@QFN44(ISP)(Low-V) [CX0001]  
PIC18F45K20@QFN44(ML) [CX4019]  
PIC18F45K20@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F45K20@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18F45K20@TQFP44 [CX3003]  
PIC18F45K20@TQFP44(ISP)(High-V) [CX0001]  
PIC18F45K20@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F45K20@UQFN40 [CX4039] PIC18F45K22 [CX0001]  
PIC18F45K22(ISP)(H-V) [CX0001] PIC18F45K22@QFN44 [CX4018]  
PIC18F45K22@QFN44(ISP)(H-V) [CX0001]  
PIC18F45K22@QFN44(ML) [CX4019]  
PIC18F45K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F45K22@TQFP44 [CX3003]  
PIC18F45K22@TQFP44(ISP)(H-V) [CX0001]  
PIC18F45K22@UQFN40 [CX4039] PIC18F45K50 [CX0001]  
PIC18F45K50@ISP [CX0001] PIC18F45K50@QFN44 [CX4019]  
PIC18F45K50@TQFP44 [CX3003] PIC18F45K50@UQFN40 [CX4039]  
PIC18F45K80 [CX0001] PIC18F45K80(ISP) [CX0001]  
PIC18F45K80@QFN44 [CX4019] PIC18F45K80@QFN44(ISP) [CX0001]

PIC18F45K80@TQFP44 [CX3003] PIC18F45K80@TQFP44(ISP) [CX0001]  
PIC18F4610 [CX0001] PIC18F4610(ISP)(Low-V) [CX0001]  
PIC18F4610@QFN44 [CX4018]  
PIC18F4610@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4610@QFN44(ML) [CX4019]  
PIC18F4610@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4610@TQFP44 [CX3003]  
PIC18F4610@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4620 [CX0001] PIC18F4620(ISP)(Low-V) [CX0001]  
PIC18F4620@QFN44 [CX4018]  
PIC18F4620@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4620@QFN44(ML) [CX4019]  
PIC18F4620@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4620@TQFP44 [CX3003]  
PIC18F4620@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4680 [CX0001] PIC18F4680(ISP)(High-V) [CX0001]  
PIC18F4680(ISP)(Low-V) [CX0001] PIC18F4680@QFN44 [CX4018]  
PIC18F4680@QFN44(ISP)(High-V) [CX0001]  
PIC18F4680@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4680@QFN44(ML) [CX4019]  
PIC18F4680@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4680@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4680@TQFP44 [CX3003]  
PIC18F4680@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4680@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4682 [CX0001] PIC18F4682(ISP)(High-V) [CX0001]  
PIC18F4682(ISP)(Low-V) [CX0001] PIC18F4682@QFN44 [CX4018]  
PIC18F4682@QFN44(ISP)(High-V) [CX0001]  
PIC18F4682@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4682@QFN44(ML) [CX4019]  
PIC18F4682@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4682@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4682@TQFP44 [CX3003]  
PIC18F4682@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4682@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F4685 [CX0001] PIC18F4685(ISP)(High-V) [CX0001]  
PIC18F4685(ISP)(Low-V) [CX0001] PIC18F4685@QFN44 [CX4018]  
PIC18F4685@QFN44(ISP)(High-V) [CX0001]  
PIC18F4685@QFN44(ISP)(Low-V) [CX0001]  
PIC18F4685@QFN44(ML) [CX4019]  
PIC18F4685@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F4685@QFN44(ML)(ISP)(Low-V) [CX0001]  
PIC18F4685@TQFP44 [CX3003]  
PIC18F4685@TQFP44(ISP)(High-V) [CX0001]  
PIC18F4685@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F46J11 [CX0001] PIC18F46J11(ISP) [CX0001]  
PIC18F46J11@QFN44 [CX4018] PIC18F46J11@QFN44(ISP) [CX0001]  
PIC18F46J11@QFN44(ML) [CX4019]  
PIC18F46J11@QFN44(ML)(ISP) [CX0001]  
PIC18F46J11@TQFP44 [CX3003] PIC18F46J11@TQFP44(ISP) [CX0001]  
PIC18F46J13 [CX0001] PIC18F46J13(ISP) [CX0001]  
PIC18F46J13@QFN44 [CX4018] PIC18F46J13@QFN44(ISP) [CX0001]  
PIC18F46J13@QFN44(ML) [CX4019]  
PIC18F46J13@QFN44(ML)(ISP) [CX0001]  
PIC18F46J13@TQFP44 [CX3003] PIC18F46J13@TQFP44(ISP) [CX0001]  
PIC18F46J50 [CX0001] PIC18F46J50(ISP) [CX0001]  
PIC18F46J50@QFN44 [CX4018] PIC18F46J50@QFN44(ISP) [CX0001]  
PIC18F46J50@QFN44(ML) [CX4019]  
PIC18F46J50@QFN44(ML)(ISP) [CX0001]

PIC18F46J50@TQFP44 [CX3003] PIC18F46J50@TQFP44(ISP) [CX0001]  
PIC18F46J53 [CX0001] PIC18F46J53(ISP) [CX0001]  
PIC18F46J53@QFN44 [CX4018] PIC18F46J53@QFN44(ISP) [CX0001]  
PIC18F46J53@QFN44(ML) [CX4019]  
PIC18F46J53@QFN44(ML)(ISP) [CX0001]  
PIC18F46J53@TQFP44 [CX3003] PIC18F46J53@TQFP44(ISP) [CX0001]  
PIC18F46K20 [CX0001]  
PIC18F46K20(ISP)(High-V) [CX0001]  
PIC18F46K20(ISP)(Low-V) [CX0001] PIC18F46K20@QFN44 [CX4018]  
PIC18F46K20@QFN44(ISP)(High-V) [CX0001]  
PIC18F46K20@QFN44(ISP)(Low-V) [CX0001]  
PIC18F46K20@QFN44(ML) [CX4019]  
PIC18F46K20@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F46K20@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18F46K20@TQFP44 [CX3003]  
PIC18F46K20@TQFP44(ISP)(High-V) [CX0001]  
PIC18F46K20@TQFP44(ISP)(Low-V) [CX0001]  
PIC18F46K20@UQFN40 [CX4039] PIC18F46K22 [CX0001]  
PIC18F46K22(ISP)(H-V) [CX0001] PIC18F46K22@QFN44 [CX4018]  
PIC18F46K22@QFN44(ISP)(H-V) [CX0001]  
PIC18F46K22@QFN44(ML) [CX4019]  
PIC18F46K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18F46K22@TQFP44 [CX3003]  
PIC18F46K22@TQFP44(ISP)(H-V) [CX0001]  
PIC18F46K22@UQFN40 [CX4039] PIC18F46K50 [CX0001]  
PIC18F46K50@ISP [CX0001] PIC18F46K50@QFN44 [CX4019]  
PIC18F46K50@TQFP44 [CX3003] PIC18F46K50@UQFN40 [CX4039]  
PIC18F46K80 [CX0001] PIC18F46K80(ISP) [CX0001]  
PIC18F46K80@QFN44 [CX4019] PIC18F46K80@QFN44(ISP) [CX0001]  
PIC18F46K80@TQFP44 [CX3003] PIC18F46K80@TQFP44(ISP) [CX0001]  
PIC18F47J13 [CX0001] PIC18F47J13(ISP) [CX0001]  
PIC18F47J13@QFN44 [CX4018] PIC18F47J13@QFN44(ISP) [CX0001]  
PIC18F47J13@QFN44(ML) [CX4019]  
PIC18F47J13@QFN44(ML)(ISP) [CX0001]  
PIC18F47J13@TQFP44 [CX3003] PIC18F47J13@TQFP44(ISP) [CX0001]  
PIC18F47J53 [CX0001] PIC18F47J53(ISP) [CX0001]  
PIC18F47J53@QFN44 [CX4018] PIC18F47J53@QFN44(ISP) [CX0001]  
PIC18F47J53@QFN44(ML) [CX4019]  
PIC18F47J53@QFN44(ML)(ISP) [CX0001]  
PIC18F47J53@TQFP44 [CX3003] PIC18F47J53@TQFP44(ISP) [CX0001]  
PIC18F6310@TQFP64 [CX3011] PIC18F6310@TQFP64(ISP) [CX0001]  
PIC18F6390@TQFP64 [CX3011] PIC18F6390@TQFP64(ISP) [CX0001]  
PIC18F6393@TQFP64 [CX3011] PIC18F6393@TQFP64(ISP) [CX0001]  
PIC18F63J11@TQFP64 [CX3011] PIC18F63J11@TQFP64(ISP) [CX0001]  
PIC18F63J90@TQFP64 [CX3011] PIC18F63J90@TQFP64(ISP) [CX0001]  
PIC18F6410@TQFP64 [CX3011] PIC18F6410@TQFP64(ISP) [CX0001]  
PIC18F6490@TQFP64 [CX3011] PIC18F6490@TQFP64(ISP) [CX0001]  
PIC18F6493@TQFP64 [CX3011] PIC18F6493@TQFP64(ISP) [CX0001]  
PIC18F64J11@TQFP64 [CX3011] PIC18F64J11@TQFP64(ISP) [CX0001]  
PIC18F64J90@TQFP64 [CX3011] PIC18F64J90@TQFP64(ISP) [CX0001]  
PIC18F6520@TQFP64 [CX3011] PIC18F6520@TQFP64(ISP) [CX0001]  
PIC18F6525@TQFP64 [CX3011] PIC18F6525@TQFP64(ISP) [CX0001]  
PIC18F6527@TQFP64 [CX3011]  
PIC18F6527@TQFP64(ISP)(High-V) [CX0001]  
PIC18F6527@TQFP64(ISP)(Low-V) [CX0001]  
PIC18F6585@PLCC68 [CX2068] PIC18F6585@PLCC68(ISP) [CX0001]  
PIC18F6585@TQFP64 [CX3011] PIC18F6585@TQFP64(ISP) [CX0001]  
PIC18F65J10@TQFP64 [CX3011] PIC18F65J10@TQFP64(ISP) [CX0001]  
PIC18F65J10@TQFP64(ISP)(Enable) [CX0001]

PIC18F65J11@TQFP64 [CX3011] PIC18F65J11@TQFP64(ISP) [CX0001]  
PIC18F65J15@TQFP64 [CX3011] PIC18F65J15@TQFP64(ISP) [CX0001]  
PIC18F65J15@TQFP64(ISP)(Enable) [CX0001]  
PIC18F65J50@TQFP64 [CX3011] PIC18F65J50@TQFP64(ISP) [CX0001]  
PIC18F65J90@TQFP64 [CX3011] PIC18F65J90@TQFP64(ISP) [CX0001]  
PIC18F65K22(HVISP)(Disable) [CX0001]  
PIC18F65K22(HVISP)(Enable) [CX0001]  
PIC18F65K22(LVISP)(Disable) [CX0001]  
PIC18F65K22(LVISP)(Enable) [CX0001]  
PIC18F65K22@TQFP64(HV) [CX3011] PIC18F65K22@TQFP64(LV) [CX3011]  
PIC18F65K80@QFN64 [CX4023] PIC18F65K80@QFN64(ISP) [CX0001]  
PIC18F65K80@TQFP64 [CX3011] PIC18F65K80@TQFP64(ISP) [CX0001]  
PIC18F65K90(HVISP)(Disable) [CX0001]  
PIC18F65K90(HVISP)(Enable) [CX0001]  
PIC18F65K90(LVISP)(Disable) [CX0001]  
PIC18F65K90(LVISP)(Enable) [CX0001]  
PIC18F65K90@TQFP64(HV) [CX3011] PIC18F65K90@TQFP64(LV) [CX3011]  
PIC18F6620@TQFP64 [CX3011] PIC18F6620@TQFP64(ISP) [CX0001]  
PIC18F6621@TQFP64 [CX3011] PIC18F6621@TQFP64(ISP) [CX0001]  
PIC18F6622@TQFP64 [CX3011]  
PIC18F6622@TQFP64(ISP)(High-V) [CX0001]  
PIC18F6622@TQFP64(ISP)(Low-V) [CX0001]  
PIC18F6627@TQFP64 [CX3011]  
PIC18F6627@TQFP64(ISP)(High-V) [CX0001]  
PIC18F6627@TQFP64(ISP)(Low-V) [CX0001]  
PIC18F6628@TQFP64 [CX3011]  
PIC18F6628@TQFP64(ISP)(High-V) [CX0001]  
PIC18F6628@TQFP64(ISP)(Low-V) [CX0001]  
PIC18F6680@PLCC68 [CX2068] PIC18F6680@PLCC68(ISP) [CX0001]  
PIC18F6680@TQFP64 [CX3011] PIC18F6680@TQFP64(ISP) [CX0001]  
PIC18F66J10@TQFP64 [CX3011] PIC18F66J10@TQFP64(ISP) [CX0001]  
PIC18F66J10@TQFP64(ISP)(Enable) [CX0001]  
PIC18F66J11@TQFP64 [CX3011] PIC18F66J11@TQFP64(ISP) [CX0001]  
PIC18F66J15@TQFP64 [CX3011] PIC18F66J15@TQFP64(ISP) [CX0001]  
PIC18F66J15@TQFP64(ISP)(Enable) [CX0001]  
PIC18F66J16@TQFP64 [CX3011] PIC18F66J16@TQFP64(ISP) [CX0001]  
PIC18F66J50@TQFP64 [CX3011] PIC18F66J50@TQFP64(ISP) [CX0001]  
PIC18F66J55@TQFP64 [CX3011] PIC18F66J55@TQFP64(ISP) [CX0001]  
PIC18F66J60@TQFP64 [CX3011] PIC18F66J60@TQFP64(ISP) [CX0001]  
PIC18F66J65@TQFP64 [CX3011] PIC18F66J65@TQFP64(ISP) [CX0001]  
PIC18F66J90@TQFP64 [CX3011] PIC18F66J90@TQFP64(ISP) [CX0001]  
PIC18F66J93@TQFP64 [CX3011] PIC18F66J93@TQFP64(ISP) [CX0001]  
PIC18F66K22(HVISP)(Disable) [CX0001]  
PIC18F66K22(HVISP)(Enable) [CX0001]  
PIC18F66K22(LVISP)(Disable) [CX0001]  
PIC18F66K22(LVISP)(Enable) [CX0001]  
PIC18F66K22@TQFP64(HV) [CX3011] PIC18F66K22@TQFP64(LV) [CX3011]  
PIC18F66K80@QFN64 [CX4023] PIC18F66K80@QFN64(ISP) [CX0001]  
PIC18F66K80@TQFP64 [CX3011] PIC18F66K80@TQFP64(ISP) [CX0001]  
PIC18F66K90(HVISP)(Disable) [CX0001]  
PIC18F66K90(HVISP)(Enable) [CX0001]  
PIC18F66K90(LVISP)(Disable) [CX0001]  
PIC18F66K90(LVISP)(Enable) [CX0001]  
PIC18F66K90@TQFP64(HV) [CX3011] PIC18F66K90@TQFP64(LV) [CX3011]  
PIC18F6720(MEXICO)@TQFP64 [CX3011]  
PIC18F6720@TQFP64 [CX3011] PIC18F6720@TQFP64(ISP) [CX0001]  
PIC18F6722@TQFP64 [CX3011]  
PIC18F6722@TQFP64(ISP)(High-V) [CX0001]  
PIC18F6722@TQFP64(ISP)(Low-V) [CX0001]

PIC18F6723@TQFP64 [CX3011]  
PIC18F6723@TQFP64(ISP)(High-V) [CX0001]  
PIC18F6723@TQFP64(ISP)(Low-V) [CX0001]  
PIC18F67J10@TQFP64 [CX3011] PIC18F67J10@TQFP64(ISP) [CX0001]  
PIC18F67J10@TQFP64(ISP)(Enable) [CX0001]  
PIC18F67J11@TQFP64 [CX3011] PIC18F67J11@TQFP64(ISP) [CX0001]  
PIC18F67J50@TQFP64 [CX3011] PIC18F67J50@TQFP64(ISP) [CX0001]  
PIC18F67J60@TQFP64 [CX3011] PIC18F67J60@TQFP64(ISP) [CX0001]  
PIC18F67J90@TQFP64 [CX3011] PIC18F67J90@TQFP64(ISP) [CX0001]  
PIC18F67J93@TQFP64 [CX3011] PIC18F67J93@TQFP64(ISP) [CX0001]  
PIC18F67K22(HVISP)(Disable) [CX0001]  
PIC18F67K22(HVISP)(Enable) [CX0001]  
PIC18F67K22(LVISP)(Disable) [CX0001]  
PIC18F67K22(LVISP)(Enable) [CX0001]  
PIC18F67K22@TQFP64(HV) [CX3011] PIC18F67K22@TQFP64(LV) [CX3011]  
PIC18F67K90(HVISP)(Disable) [CX0001]  
PIC18F67K90(HVISP)(Enable) [CX0001]  
PIC18F67K90(LVISP)(Disable) [CX0001]  
PIC18F67K90(LVISP)(Enable) [CX0001]  
PIC18F67K90@TQFP64(HV) [CX3011] PIC18F67K90@TQFP64(LV) [CX3011]  
PIC18F8310@TQFP80 [CX3016] PIC18F8310@TQFP80(ISP) [CX0001]  
PIC18F8390@TQFP80 [CX3016] PIC18F8390@TQFP80(ISP) [CX0001]  
PIC18F8393@TQFP80 [CX3016] PIC18F8393@TQFP80(ISP) [CX0001]  
PIC18F83J11@TQFP80 [CX3016] PIC18F83J11@TQFP80(ISP) [CX0001]  
PIC18F83J90@TQFP80 [CX3016] PIC18F83J90@TQFP80(ISP) [CX0001]  
PIC18F8410@TQFP80 [CX3016] PIC18F8410@TQFP80(ISP) [CX0001]  
PIC18F8490@TQFP80 [CX3016] PIC18F8490@TQFP80(ISP) [CX0001]  
PIC18F8493@TQFP80 [CX3016] PIC18F8493@TQFP80(ISP) [CX0001]  
PIC18F84J11@TQFP80 [CX3016] PIC18F84J11@TQFP80(ISP) [CX0001]  
PIC18F84J90@TQFP80 [CX3016] PIC18F84J90@TQFP80(ISP) [CX0001]  
PIC18F8520@TQFP80 [CX3016] PIC18F8520@TQFP80(ISP) [CX0001]  
PIC18F8525@TQFP80 [CX3016] PIC18F8525@TQFP80(ISP) [CX0001]  
PIC18F8527@TQFP80 [CX3016]  
PIC18F8527@TQFP80(ISP)(High-V) [CX0001]  
PIC18F8527@TQFP80(ISP)(Low-V) [CX0001]  
PIC18F8585@TQFP80 [CX3016] PIC18F8585@TQFP80(ISP) [CX0001]  
PIC18F85J10@TQFP80 [CX3016] PIC18F85J10@TQFP80(ISP) [CX0001]  
PIC18F85J10@TQFP80(ISP)(Enable) [CX0001]  
PIC18F85J11@TQFP80 [CX3016] PIC18F85J11@TQFP80(ISP) [CX0001]  
PIC18F85J15@TQFP80 [CX3016] PIC18F85J15@TQFP80(ISP) [CX0001]  
PIC18F85J15@TQFP80(ISP)(Enable) [CX0001]  
PIC18F85J50@TQFP80 [CX3016] PIC18F85J50@TQFP80(ISP) [CX0001]  
PIC18F85J90@TQFP80 [CX3016] PIC18F85J90@TQFP80(ISP) [CX0001]  
PIC18F85K22(HVISP)(Disable) [CX0001]  
PIC18F85K22(HVISP)(Enable) [CX0001]  
PIC18F85K22(LVISP)(Disable) [CX0001]  
PIC18F85K22(LVISP)(Enable) [CX0001]  
PIC18F85K22@TQFP80(HV) [CX3016] PIC18F85K22@TQFP80(LV) [CX3016]  
PIC18F85K90(HVISP)(Disable) [CX0001]  
PIC18F85K90(HVISP)(Enable) [CX0001]  
PIC18F85K90(LVISP)(Disable) [CX0001]  
PIC18F85K90(LVISP)(Enable) [CX0001]  
PIC18F85K90@TQFP80(HV) [CX3016] PIC18F85K90@TQFP80(LV) [CX3016]  
PIC18F8620@TQFP80 [CX3016] PIC18F8620@TQFP80(ISP) [CX0001]  
PIC18F8621@TQFP80 [CX3016] PIC18F8621@TQFP80(ISP) [CX0001]  
PIC18F8622@TQFP80 [CX3016]  
PIC18F8622@TQFP80(ISP)(High-V) [CX0001]  
PIC18F8622@TQFP80(ISP)(Low-V) [CX0001]  
PIC18F8627@TQFP80 [CX3016]



PIC18F8627@TQFP80(ISP)(High-V) [CX0001]  
PIC18F8627@TQFP80(ISP)(Low-V) [CX0001]  
PIC18F8628@TQFP80 [CX3016]  
PIC18F8628@TQFP80(ISP)(High-V) [CX0001]  
PIC18F8628@TQFP80(ISP)(Low-V) [CX0001]  
PIC18F8680@TQFP80 [CX3016] PIC18F8680@TQFP80(ISP) [CX0001]  
PIC18F86J10@TQFP80 [CX3016] PIC18F86J10@TQFP80(ISP) [CX0001]  
PIC18F86J10@TQFP80(ISP)(Enable) [CX0001]  
PIC18F86J11@TQFP80 [CX3016] PIC18F86J11@TQFP80(ISP) [CX0001]  
PIC18F86J15@TQFP80 [CX3016] PIC18F86J15@TQFP80(ISP) [CX0001]  
PIC18F86J15@TQFP80(ISP)(Enable) [CX0001]  
PIC18F86J16@TQFP80 [CX3016] PIC18F86J16@TQFP80(ISP) [CX0001]  
PIC18F86J50@TQFP80 [CX3016] PIC18F86J50@TQFP80(ISP) [CX0001]  
PIC18F86J55@TQFP80 [CX3016] PIC18F86J55@TQFP80(ISP) [CX0001]  
PIC18F86J60@TQFP80 [CX3016] PIC18F86J60@TQFP80(ISP) [CX0001]  
PIC18F86J65@TQFP80 [CX3016] PIC18F86J65@TQFP80(ISP) [CX0001]  
PIC18F86J72@TQFP80 [CX3016] PIC18F86J72@TQFP80(ISP) [CX0001]  
PIC18F86J72@TQFP80(ISP)(Enable) [CX0001]  
PIC18F86J90@TQFP80 [CX3016] PIC18F86J90@TQFP80(ISP) [CX0001]  
PIC18F86J93@TQFP80 [CX3016] PIC18F86J93@TQFP80(ISP) [CX0001]  
PIC18F86K22(HVISP)(Disable) [CX0001]  
PIC18F86K22(HVISP)(Enable) [CX0001]  
PIC18F86K22(LVISP)(Disable) [CX0001]  
PIC18F86K22(LVISP)(Enable) [CX0001]  
PIC18F86K22@TQFP80(HV) [CX3016] PIC18F86K22@TQFP80(LV) [CX3016]  
PIC18F86K90(HVISP)(Disable) [CX0001]  
PIC18F86K90(HVISP)(Enable) [CX0001]  
PIC18F86K90(LVISP)(Disable) [CX0001]  
PIC18F86K90(LVISP)(Enable) [CX0001]  
PIC18F86K90@TQFP80(HV) [CX3016] PIC18F86K90@TQFP80(LV) [CX3016]  
PIC18F8720@TQFP80 [CX3016] PIC18F8720@TQFP80(ISP) [CX0001]  
PIC18F8722@TQFP80 [CX3016]  
PIC18F8722@TQFP80(ISP)(High-V) [CX0001]  
PIC18F8722@TQFP80(ISP)(Low-V) [CX0001]  
PIC18F8723@TQFP80 [CX3016]  
PIC18F8723@TQFP80(ISP)(High-V) [CX0001]  
PIC18F8723@TQFP80(ISP)(Low-V) [CX0001]  
PIC18F87J10@TQFP80 [CX3016] PIC18F87J10@TQFP80(ISP) [CX0001]  
PIC18F87J10@TQFP80(ISP)(Enable) [CX0001]  
PIC18F87J11@TQFP80 [CX3016] PIC18F87J11@TQFP80(ISP) [CX0001]  
PIC18F87J50@TQFP80 [CX3016] PIC18F87J50@TQFP80(ISP) [CX0001]  
PIC18F87J60@TQFP80 [CX3016] PIC18F87J60@TQFP80(ISP) [CX0001]  
PIC18F87J72@TQFP80 [CX3016] PIC18F87J72@TQFP80(ISP) [CX0001]  
PIC18F87J72@TQFP80(ISP)(Enable) [CX0001]  
PIC18F87J90@TQFP80 [CX3016] PIC18F87J90@TQFP80(ISP) [CX0001]  
PIC18F87J93@TQFP80 [CX3016] PIC18F87J93@TQFP80(ISP) [CX0001]  
PIC18F87K22(HVISP)(Disable) [CX0001]  
PIC18F87K22(HVISP)(Enable) [CX0001]  
PIC18F87K22(LVISP)(Disable) [CX0001]  
PIC18F87K22(LVISP)(Enable) [CX0001]  
PIC18F87K22@TQFP80(HV) [CX3016] PIC18F87K22@TQFP80(LV) [CX3016]  
PIC18F87K90(HVISP)(Disable) [CX0001]  
PIC18F87K90(HVISP)(Enable) [CX0001]  
PIC18F87K90(LVISP)(Disable) [CX0001]  
PIC18F87K90(LVISP)(Enable) [CX0001]  
PIC18F87K90@TQFP80(HV) [CX3016] PIC18F87K90@TQFP80(LV) [CX3016]  
PIC18F96J60@TQFP100(ISP) [CX0001]  
PIC18F96J60@TQFP100[12\*12\*1] [CX3071]  
PIC18F96J60@TQFP100[14\*14\*1] [CX3021]

PIC18F96J65@TQFP100(ISP) [CX0001]  
PIC18F96J65@TQFP100[12\*12\*1] [CX3071]  
PIC18F96J65@TQFP100[14\*14\*1] [CX3021]  
PIC18F97J60@TQFP100(ISP) [CX0001]  
PIC18F97J60@TQFP100[12\*12\*1] [CX3071]  
PIC18F97J60@TQFP100[14\*14\*1] [CX3021]  
PIC18LC452 [CX0001] PIC18LC452@PLCC44 [CX2044]  
PIC18LC452@TQFP44 [CX3003] PIC18LF1220 [CX0001]  
PIC18LF1220(ISP) [CX0001] PIC18LF1220@QFN28 [CX4014]  
PIC18LF1220@SOIC18 [CX1033] PIC18LF1220@SOIC18(ISP) [CX0001]  
PIC18LF1220@SSOP20 [CX1026] PIC18LF1220@SSOP20(ISP) [CX0001]  
PIC18LF1320 [CX0001] PIC18LF1320(ISP) [CX0001]  
PIC18LF1320@QFN28 [CX4014] PIC18LF1320@SOIC18 [CX1033]  
PIC18LF1320@SOIC18(ISP) [CX0001] PIC18LF1320@SSOP20 [CX1026]  
PIC18LF1320@SSOP20(ISP) [CX0001] PIC18LF13K22 [CX0001]  
PIC18LF13K22(ISP)(High-V) [CX0001]  
PIC18LF13K22(ISP)(Low-V) [CX0001]  
PIC18LF13K22@QFN20 [CX4011]  
PIC18LF13K22@QFN20(ISP)(High-V) [CX0001]  
PIC18LF13K22@QFN20(ISP)(Low-V) [CX0001]  
PIC18LF13K22@SOIC20 [CX1033]  
PIC18LF13K22@SOIC20(ISP)(High-V) [CX0001]  
PIC18LF13K22@SOIC20(ISP)(Low-V) [CX0001]  
PIC18LF13K22@SSOP20 [CX1026]  
PIC18LF13K22@SSOP20(ISP)(High-V) [CX0001]  
PIC18LF13K22@SSOP20(ISP)(Low-V) [CX0001]  
PIC18LF13K50 [CX0001]  
PIC18LF13K50(ISP)(High-V) [CX0001]  
PIC18LF13K50(ISP)(Low-V) [CX0001]  
PIC18LF13K50@QFN20 [CX4025]  
PIC18LF13K50@QFN20(ISP)(High-V) [CX0001]  
PIC18LF13K50@QFN20(ISP)(Low-V) [CX0001]  
PIC18LF13K50@SOIC20 [CX1033]  
PIC18LF13K50@SOIC20(ISP)(High-V) [CX0001]  
PIC18LF13K50@SOIC20(ISP)(Low-V) [CX0001]  
PIC18LF13K50@SSOP20 [CX1026]  
PIC18LF13K50@SSOP20(ISP)(High-V) [CX0001]  
PIC18LF13K50@SSOP20(ISP)(Low-V) [CX0001]  
PIC18LF14K22 [CX0001]  
PIC18LF14K22(ISP)(High-V) [CX0001]  
PIC18LF14K22(ISP)(Low-V) [CX0001]  
PIC18LF14K22@QFN20 [CX4011]  
PIC18LF14K22@QFN20(ISP)(High-V) [CX0001]  
PIC18LF14K22@QFN20(ISP)(Low-V) [CX0001]  
PIC18LF14K22@SOIC20 [CX1033]  
PIC18LF14K22@SOIC20(ISP)(High-V) [CX0001]  
PIC18LF14K22@SOIC20(ISP)(Low-V) [CX0001]  
PIC18LF14K22@SSOP20 [CX1026]  
PIC18LF14K22@SSOP20(ISP)(High-V) [CX0001]  
PIC18LF14K22@SSOP20(ISP)(Low-V) [CX0001]  
PIC18LF14K50 [CX0001]  
PIC18LF14K50(ISP)(High-V) [CX0001]  
PIC18LF14K50(ISP)(Low-V) [CX0001]  
PIC18LF14K50@QFN20 [CX4025]  
PIC18LF14K50@QFN20(ISP)(High-V) [CX0001]  
PIC18LF14K50@QFN20(ISP)(Low-V) [CX0001]  
PIC18LF14K50@SOIC20 [CX1033]  
PIC18LF14K50@SOIC20(ISP)(High-V) [CX0001]  
PIC18LF14K50@SOIC20(ISP)(Low-V) [CX0001]

PIC18LF14K50@SSOP20 [CX1026]  
PIC18LF14K50@SSOP20(ISP)(High-V) [CX0001]  
PIC18LF14K50@SSOP20(ISP)(Low-V) [CX0001]  
PIC18LF2220 [CX0001] PIC18LF2220(ISP) [CX0001]  
PIC18LF2220@SOIC28 [CX1033] PIC18LF2220@SOIC28(ISP) [CX0001]  
PIC18LF2221 [CX0001] PIC18LF2221(ISP)(Low-V) [CX0001]  
PIC18LF2221@QFN28 [CX4014]  
PIC18LF2221@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2221@SOIC28 [CX1033]  
PIC18LF2221@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2221@SSOP28 [CX1026]  
PIC18LF2221@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2320 [CX0001] PIC18LF2320(ISP) [CX0001]  
PIC18LF2320@SOIC28 [CX1033] PIC18LF2320@SOIC28(ISP) [CX0001]  
PIC18LF2321 [CX0001] PIC18LF2321(ISP)(Low-V) [CX0001]  
PIC18LF2321@QFN28 [CX4014]  
PIC18LF2321@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2321@SOIC28 [CX1033]  
PIC18LF2321@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2321@SSOP28 [CX1026]  
PIC18LF2321@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2331 [CX0001] PIC18LF2331(ISP) [CX0001]  
PIC18LF2331@SOIC28 [CX1033] PIC18LF2331@SOIC28(ISP) [CX0001]  
PIC18LF23K22 [CX0001] PIC18LF23K22(ISP)(H-V) [CX0001]  
PIC18LF23K22@QFN28 [CX4014]  
PIC18LF23K22@QFN28(ISP)(H-V) [CX0001]  
PIC18LF23K22@SOIC28 [CX1033]  
PIC18LF23K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18LF23K22@SSOP28 [CX1026]  
PIC18LF23K22@SSOP28(ISP)(H-V) [CX0001]  
PIC18LF23K22@UQFN28 [CX4036] PIC18LF2410 [CX0001]  
PIC18LF2410(ISP)(Low-V) [CX0001] PIC18LF2410@QFN28 [CX4014]  
PIC18LF2410@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2410@SOIC28 [CX1033]  
PIC18LF2410@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2410@SSOP28 [CX1026]  
PIC18LF2410@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF242 [CX0001] PIC18LF242(ISP) [CX0001]  
PIC18LF242@SOIC28 [CX1033] PIC18LF242@SOIC28(ISP) [CX0001]  
PIC18LF2420 [CX0001]  
PIC18LF2420(ISP)(High-V) [CX0001]  
PIC18LF2420(ISP)(Low-V) [CX0001] PIC18LF2420@QFN28 [CX4014]  
PIC18LF2420@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2420@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2420@SOIC28 [CX1033]  
PIC18LF2420@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2420@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2420@SSOP28 [CX1026]  
PIC18LF2420@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2420@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2423 [CX0001]  
PIC18LF2423(ISP)(High-V) [CX0001]  
PIC18LF2423(ISP)(Low-V) [CX0001] PIC18LF2423@QFN28 [CX4014]  
PIC18LF2423@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2423@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2423@SOIC28 [CX1033]  
PIC18LF2423@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2423@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2423@SSOP28 [CX1026]

PIC18LF2423@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2423@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2431 [CX0001] PIC18LF2431(ISP) [CX0001]  
PIC18LF2431@SOIC28 [CX1033] PIC18LF2431@SOIC28(ISP) [CX0001]  
PIC18LF2439 [CX0001] PIC18LF2439(ISP) [CX0001]  
PIC18LF2439@SOIC28 [CX1033] PIC18LF2439@SOIC28(ISP) [CX0001]  
PIC18LF2450 [CX0001] PIC18LF2450(ISP)(Low-V) [CX0001]  
PIC18LF2450@QFN28 [CX4014]  
PIC18LF2450@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2450@SOIC28 [CX1033]  
PIC18LF2450@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2450@SSOP28 [CX1026]  
PIC18LF2450@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2455 [CX0001]  
PIC18LF2455(ISP)(High-V) [CX0001]  
PIC18LF2455(ISP)(Low-V) [CX0001] PIC18LF2455@SOIC28 [CX1033]  
PIC18LF2455@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2455@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2455@SSOP28 [CX1026]  
PIC18LF2455@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2455@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF248 [CX0001] PIC18LF248(ISP) [CX0001]  
PIC18LF248@SOIC28 [CX1033] PIC18LF248@SOIC28(ISP) [CX0001]  
PIC18LF2480 [CX0001]  
PIC18LF2480(ISP)(High-V) [CX0001]  
PIC18LF2480(ISP)(Low-V) [CX0001] PIC18LF2480@QFN28 [CX4014]  
PIC18LF2480@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2480@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2480@SOIC28 [CX1033]  
PIC18LF2480@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2480@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2480@SSOP28 [CX1026]  
PIC18LF2480@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2480@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF24J10 [CX0001] PIC18LF24J10(ISP) [CX0001]  
PIC18LF24J10@QFN28 [CX4014] PIC18LF24J10@QFN28(ISP) [CX0001]  
PIC18LF24J10@SOIC28 [CX1033]  
PIC18LF24J10@SOIC28(ISP) [CX0001]  
PIC18LF24J10@SSOP28 [CX1026]  
PIC18LF24J10@SSOP28(ISP) [CX0001]  
PIC18LF24J11 [CX0001] PIC18LF24J11(ISP) [CX0001]  
PIC18LF24J11@QFN28 [CX4014] PIC18LF24J11@QFN28(ISP) [CX0001]  
PIC18LF24J11@SOIC28 [CX1033]  
PIC18LF24J11@SOIC28(ISP) [CX0001]  
PIC18LF24J11@SSOP28 [CX1026]  
PIC18LF24J11@SSOP28(ISP) [CX0001]  
PIC18LF24J50 [CX0001] PIC18LF24J50(ISP) [CX0001]  
PIC18LF24J50@QFN28 [CX4014] PIC18LF24J50@QFN28(ISP) [CX0001]  
PIC18LF24J50@SOIC28 [CX1033]  
PIC18LF24J50@SOIC28(ISP) [CX0001]  
PIC18LF24J50@SSOP28 [CX1026]  
PIC18LF24J50@SSOP28(ISP) [CX0001]  
PIC18LF24K22 [CX0001] PIC18LF24K22(ISP)(H-V) [CX0001]  
PIC18LF24K22@QFN28 [CX4014]  
PIC18LF24K22@QFN28(ISP)(H-V) [CX0001]  
PIC18LF24K22@SOIC28 [CX1033]  
PIC18LF24K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18LF24K22@SSOP28 [CX1026]  
PIC18LF24K22@SSOP28(ISP)(H-V) [CX0001]

PIC18LF24K22@UQFN28 [CX4036]                    PIC18LF24K50 [CX0001]  
PIC18LF24K50@ISP [CX0001]                    PIC18LF24K50@QFN28 [CX4014]  
PIC18LF24K50@SOIC28 [CX1033]                PIC18LF24K50@SSOP28 [CX1026]  
PIC18LF2510 [CX0001]                        PIC18LF2510(ISP) [CX0001]  
PIC18LF2510@QFN28 [CX4014]                PIC18LF2510@QFN28(ISP) [CX0001]  
PIC18LF2510@SOIC28 [CX1033]                PIC18LF2510@SOIC28(ISP) [CX0001]  
PIC18LF2510@SSOP28 [CX1026]                PIC18LF2510@SSOP28(ISP) [CX0001]  
PIC18LF2515 [CX0001]                        PIC18LF2515(ISP)(Low-V) [CX0001]  
PIC18LF2515@SOIC28 [CX1033]  
PIC18LF2515@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2515@SSOP28 [CX1026]  
PIC18LF2515@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF252 [CX0001]                        PIC18LF252(ISP) [CX0001]  
PIC18LF252@SOIC28 [CX1033]                PIC18LF252@SOIC28(ISP) [CX0001]  
PIC18LF2520 [CX0001]  
PIC18LF2520(ISP)(High-V) [CX0001]  
PIC18LF2520(ISP)(Low-V) [CX0001]        PIC18LF2520@QFN28 [CX4014]  
PIC18LF2520@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2520@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2520@SOIC28 [CX1033]  
PIC18LF2520@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2520@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2520@SSOP28 [CX1026]  
PIC18LF2520@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2520@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2523 [CX0001]  
PIC18LF2523(ISP)(High-V) [CX0001]  
PIC18LF2523(ISP)(Low-V) [CX0001]        PIC18LF2523@QFN28 [CX4014]  
PIC18LF2523@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2523@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2523@SOIC28 [CX1033]  
PIC18LF2523@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2523@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2523@SSOP28 [CX1026]  
PIC18LF2523@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2523@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2525 [CX0001]                        PIC18LF2525(ISP)(Low-V) [CX0001]  
PIC18LF2525@SOIC28 [CX1033]  
PIC18LF2525@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2525@SSOP28 [CX1026]  
PIC18LF2525@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2539 [CX0001]                        PIC18LF2539(ISP) [CX0001]  
PIC18LF2539@SOIC28 [CX1033]                PIC18LF2539@SOIC28(ISP) [CX0001]  
PIC18LF2550 [CX0001]  
PIC18LF2550(ISP)(High-V) [CX0001]  
PIC18LF2550(ISP)(Low-V) [CX0001]        PIC18LF2550@SOIC28 [CX1033]  
PIC18LF2550@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2550@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2550@SSOP28 [CX1026]  
PIC18LF2550@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2550@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF258 [CX0001]                        PIC18LF258(ISP) [CX0001]  
PIC18LF258@SOIC28 [CX1033]                PIC18LF258@SOIC28(ISP) [CX0001]  
PIC18LF2580 [CX0001]  
PIC18LF2580(ISP)(High-V) [CX0001]  
PIC18LF2580(ISP)(Low-V) [CX0001]        PIC18LF2580@QFN28 [CX4014]  
PIC18LF2580@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2580@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2580@SOIC28 [CX1033]

PIC18LF2580@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2580@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2580@SSOP28 [CX1026]  
PIC18LF2580@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2580@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2585 [CX0001]  
PIC18LF2585(ISP)(High-V) [CX0001]  
PIC18LF2585(ISP)(Low-V) [CX0001] PIC18LF2585@SDIP28 [CX0032]  
PIC18LF2585@SDIP28(ISP)(High-V) [CX0001]  
PIC18LF2585@SDIP28(ISP)(Low-V) [CX0001]  
PIC18LF2585@SOIC28 [CX1033]  
PIC18LF2585@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2585@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2585@SSOP28 [CX1026]  
PIC18LF2585@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2585@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF25J10 [CX0001] PIC18LF25J10(ISP) [CX0001]  
PIC18LF25J10@QFN28 [CX4014] PIC18LF25J10@QFN28(ISP) [CX0001]  
PIC18LF25J10@SOIC28 [CX1033]  
PIC18LF25J10@SOIC28(ISP) [CX0001]  
PIC18LF25J10@SSOP28 [CX1026]  
PIC18LF25J10@SSOP28(ISP) [CX0001]  
PIC18LF25J11 [CX0001] PIC18LF25J11(ISP) [CX0001]  
PIC18LF25J11@QFN28 [CX4014] PIC18LF25J11@QFN28(ISP) [CX0001]  
PIC18LF25J11@SOIC28 [CX1033]  
PIC18LF25J11@SOIC28(ISP) [CX0001]  
PIC18LF25J11@SSOP28 [CX1026]  
PIC18LF25J11@SSOP28(ISP) [CX0001]  
PIC18LF25J50 [CX0001] PIC18LF25J50(ISP) [CX0001]  
PIC18LF25J50@QFN28 [CX4014] PIC18LF25J50@QFN28(ISP) [CX0001]  
PIC18LF25J50@SOIC28 [CX1033]  
PIC18LF25J50@SOIC28(ISP) [CX0001]  
PIC18LF25J50@SSOP28 [CX1026]  
PIC18LF25J50@SSOP28(ISP) [CX0001]  
PIC18LF25K22 [CX0001] PIC18LF25K22(ISP)(H-V) [CX0001]  
PIC18LF25K22@QFN28 [CX4014]  
PIC18LF25K22@QFN28(ISP)(H-V) [CX0001]  
PIC18LF25K22@SOIC28 [CX1033]  
PIC18LF25K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18LF25K22@SSOP28 [CX1026]  
PIC18LF25K22@SSOP28(ISP)(H-V) [CX0001]  
PIC18LF25K22@UQFN28 [CX4036] PIC18LF25K50 [CX0001]  
PIC18LF25K50@ISP [CX0001] PIC18LF25K50@QFN28 [CX4014]  
PIC18LF25K50@SOIC28 [CX1033] PIC18LF25K50@SSOP28 [CX1026]  
PIC18LF25K80 [CX0001] PIC18LF25K80(ISP) [CX0001]  
PIC18LF25K80@QFN28 [CX4014] PIC18LF25K80@SOIC28 [CX1033]  
PIC18LF25K80@SOIC28(ISP) [CX0001]  
PIC18LF25K80@SSOP28 [CX1026]  
PIC18LF25K80@SSOP28(ISP) [CX0001]  
PIC18LF2610 [CX0001] PIC18LF2610(ISP)(Low-V) [CX0001]  
PIC18LF2610@SOIC28 [CX1033]  
PIC18LF2610@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2610@SSOP28 [CX1026]  
PIC18LF2610@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2620 [CX0001] PIC18LF2620(ISP)(Low-V) [CX0001]  
PIC18LF2620@SOIC28 [CX1033]  
PIC18LF2620@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2620@SSOP28 [CX1026]  
PIC18LF2620@SSOP28(ISP)(Low-V) [CX0001]

PIC18LF2680 [CX0001]  
PIC18LF2680(ISP)(High-V) [CX0001]  
PIC18LF2680(ISP)(Low-V) [CX0001] PIC18LF2680@SDIP28 [CX0032]  
PIC18LF2680@SDIP28(ISP)(High-V) [CX0001]  
PIC18LF2680@SDIP28(ISP)(Low-V) [CX0001]  
PIC18LF2680@SOIC28 [CX1033]  
PIC18LF2680@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2680@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2680@SSOP28 [CX1026]  
PIC18LF2680@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2680@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2682 [CX0001]  
PIC18LF2682(ISP)(High-V) [CX0001]  
PIC18LF2682(ISP)(Low-V) [CX0001] PIC18LF2682@QFN28 [CX4014]  
PIC18LF2682@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2682@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2682@SOIC28 [CX1033]  
PIC18LF2682@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2682@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2682@SSOP28 [CX1026]  
PIC18LF2682@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2682@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF2685 [CX0001]  
PIC18LF2685(ISP)(High-V) [CX0001]  
PIC18LF2685(ISP)(Low-V) [CX0001] PIC18LF2685@QFN28 [CX4014]  
PIC18LF2685@QFN28(ISP)(High-V) [CX0001]  
PIC18LF2685@QFN28(ISP)(Low-V) [CX0001]  
PIC18LF2685@SOIC28 [CX1033]  
PIC18LF2685@SOIC28(ISP)(High-V) [CX0001]  
PIC18LF2685@SOIC28(ISP)(Low-V) [CX0001]  
PIC18LF2685@SSOP28 [CX1026]  
PIC18LF2685@SSOP28(ISP)(High-V) [CX0001]  
PIC18LF2685@SSOP28(ISP)(Low-V) [CX0001]  
PIC18LF26J11 [CX0001] PIC18LF26J11(ISP) [CX0001]  
PIC18LF26J11@QFN28 [CX4014] PIC18LF26J11@QFN28(ISP) [CX0001]  
PIC18LF26J11@SOIC28 [CX1033]  
PIC18LF26J11@SOIC28(ISP) [CX0001]  
PIC18LF26J11@SSOP28 [CX1026]  
PIC18LF26J11@SSOP28(ISP) [CX0001]  
PIC18LF26J13 [CX0001] PIC18LF26J13(ISP) [CX0001]  
PIC18LF26J13@QFN28 [CX4014] PIC18LF26J13@QFN28(ISP) [CX0001]  
PIC18LF26J13@SOIC28 [CX1033]  
PIC18LF26J13@SOIC28(ISP) [CX0001]  
PIC18LF26J13@SSOP28 [CX1026]  
PIC18LF26J13@SSOP28(ISP) [CX0001]  
PIC18LF26J50 [CX0001] PIC18LF26J50(ISP) [CX0001]  
PIC18LF26J50@QFN28 [CX4014] PIC18LF26J50@QFN28(ISP) [CX0001]  
PIC18LF26J50@SOIC28 [CX1026]  
PIC18LF26J50@SOIC28(ISP) [CX0001]  
PIC18LF26J50@SSOP28  
PIC18LF26J50@SSOP28(ISP) [CX0001]  
PIC18LF26J53 [CX0001] PIC18LF26J53(ISP) [CX0001]  
PIC18LF26J53@QFN28 [CX4014] PIC18LF26J53@QFN28(ISP) [CX0001]  
PIC18LF26J53@SOIC28 [CX1033]  
PIC18LF26J53@SOIC28(ISP) [CX0001]  
PIC18LF26J53@SSOP28 [CX1026]  
PIC18LF26J53@SSOP28(ISP) [CX0001]  
PIC18LF26K22 [CX0001] PIC18LF26K22(ISP)(H-V) [CX0001]  
PIC18LF26K22@QFN28 [CX4014]

PIC18LF26K22@QFN28(ISP)(H-V) [CX0001]  
PIC18LF26K22@SOIC28 [CX1033]  
PIC18LF26K22@SOIC28(ISP)(H-V) [CX0001]  
PIC18LF26K22@SSOP28 [CX1026]  
PIC18LF26K22@SSOP28(ISP)(H-V) [CX0001]  
PIC18LF26K22@UQFN28 [CX4036] PIC18LF26K50 [CX0001]  
PIC18LF26K50@ISP [CX0001] PIC18LF26K50@QFN28 [CX4014]  
PIC18LF26K50@SOIC28 [CX1033] PIC18LF26K50@SSOP28 [CX1026]  
PIC18LF26K80 [CX0001] PIC18LF26K80(ISP) [CX0001]  
PIC18LF26K80@QFN28 [CX4014] PIC18LF26K80@QFN28(ISP) [CX0001]  
PIC18LF26K80@SOIC28 [CX1033]  
PIC18LF26K80@SOIC28(ISP) [CX0001]  
PIC18LF26K80@SSOP28 [CX1026]  
PIC18LF26K80@SSOP28(ISP) [CX0001]  
PIC18LF27J13 [CX0001] PIC18LF27J13(ISP) [CX0001]  
PIC18LF27J13@QFN28 [CX4014] PIC18LF27J13@QFN28(ISP) [CX0001]  
PIC18LF27J13@SOIC28 [CX1033]  
PIC18LF27J13@SOIC28(ISP) [CX0001]  
PIC18LF27J13@SSOP28 [CX1026]  
PIC18LF27J13@SSOP28(ISP) [CX0001]  
PIC18LF27J53 [CX0001] PIC18LF27J53(ISP) [CX0001]  
PIC18LF27J53@QFN28 [CX4014] PIC18LF27J53@QFN28(ISP) [CX0001]  
PIC18LF27J53@SOIC28 [CX1033]  
PIC18LF27J53@SOIC28(ISP) [CX0001]  
PIC18LF27J53@SSOP28 [CX1026]  
PIC18LF27J53@SSOP28(ISP) [CX0001]  
PIC18LF4220 [CX0001] PIC18LF4220(ISP) [CX0001]  
PIC18LF4220@QFN44 [CX4018] PIC18LF4220@QFN44(ISP) [CX0001]  
PIC18LF4220@QFN44(ML) [CX4019]  
PIC18LF4220@QFN44(ML)(ISP) [CX0001]  
PIC18LF4220@TQFP44 [CX3003] PIC18LF4220@TQFP44(ISP) [CX0001]  
PIC18LF4221 [CX0001] PIC18LF4221(ISP)(Low-V) [CX0001]  
PIC18LF4221@QFN44 [CX4018]  
PIC18LF4221@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4221@QFN44(ML) [CX4019]  
PIC18LF4221@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4221@TQFP44 [CX3003]  
PIC18LF4221@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4320 [CX0001] PIC18LF4320(ISP) [CX0001]  
PIC18LF4320@QFN44 [CX4018] PIC18LF4320@QFN44(ISP) [CX0001]  
PIC18LF4320@QFN44(ML) [CX4019]  
PIC18LF4320@QFN44(ML)(ISP) [CX0001]  
PIC18LF4320@TQFP44 [CX3003] PIC18LF4320@TQFP44(ISP) [CX0001]  
PIC18LF4321 [CX0001] PIC18LF4321(ISP)(Low-V) [CX0001]  
PIC18LF4321@QFN44 [CX4018]  
PIC18LF4321@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4321@QFN44(ML) [CX4019]  
PIC18LF4321@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4321@TQFP44 [CX3003]  
PIC18LF4321@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4331 [CX0001] PIC18LF4331(ISP) [CX0001]  
PIC18LF4331@TQFP44 [CX3003] PIC18LF4331@TQFP44(ISP) [CX0001]  
PIC18LF43K22 [CX0001] PIC18LF43K22(ISP)(H-V) [CX0001]  
PIC18LF43K22@QFN44 [CX4018]  
PIC18LF43K22@QFN44(ISP)(H-V) [CX0001]  
PIC18LF43K22@QFN44(ML) [CX4019]  
PIC18LF43K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF43K22@TQFP44 [CX3003]  
PIC18LF43K22@TQFP44(ISP)(H-V) [CX0001]



PIC18LF43K22@UQFN40 [CX4039] PIC18LF4410 [CX0001]  
PIC18LF4410(ISP)(Low-V) [CX0001] PIC18LF4410@QFN44 [CX4018]  
PIC18LF4410@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4410@QFN44(ML) [CX4019]  
PIC18LF4410@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4410@TQFP44 [CX3003]  
PIC18LF4410@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF442 [CX0001] PIC18LF442(ISP) [CX0001]  
PIC18LF442@PLCC44 [CX2044] PIC18LF442@PLCC44(ISP) [CX0001]  
PIC18LF442@QFN44 [CX4019] PIC18LF442@TQFP44 [CX3003]  
PIC18LF442@TQFP44(ISP) [CX0001] PIC18LF4420 [CX0001]  
PIC18LF4420(ISP)(Low-V) [CX0001] PIC18LF4420@QFN44 [CX4018]  
PIC18LF4420@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4420@QFN44(ML) [CX4019]  
PIC18LF4420@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4420@TQFP44 [CX3003]  
PIC18LF4420@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4423 [CX0001]  
PIC18LF4423(ISP)(High-V) [CX0001]  
PIC18LF4423(ISP)(Low-V) [CX0001] PIC18LF4423@QFN44 [CX4018]  
PIC18LF4423@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4423@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4423@QFN44(ML) [CX4019]  
PIC18LF4423@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4423@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4423@TQFP44 [CX3003]  
PIC18LF4423@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4423@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4431 [CX0001] PIC18LF4431(ISP) [CX0001]  
PIC18LF4431@TQFP44 [CX3003] PIC18LF4431@TQFP44(ISP) [CX0001]  
PIC18LF4439 [CX0001] PIC18LF4439(ISP) [CX0001]  
PIC18LF4439@TQFP44 [CX3003] PIC18LF4439@TQFP44(ISP) [CX0001]  
PIC18LF4450 [CX0001] PIC18LF4450(ISP)(Low-V) [CX0001]  
PIC18LF4450@QFN44 [CX4018]  
PIC18LF4450@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4450@QFN44(ML) [CX4019]  
PIC18LF4450@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4450@TQFP44 [CX3003]  
PIC18LF4450@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4455 [CX0001]  
PIC18LF4455(ISP)(High-V) [CX0001]  
PIC18LF4455(ISP)(Low-V) [CX0001] PIC18LF4455@QFN44 [CX4018]  
PIC18LF4455@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4455@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4455@QFN44(ML) [CX4019]  
PIC18LF4455@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4455@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4455@TQFP44 [CX3003]  
PIC18LF4455@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4455@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF448 [CX0001] PIC18LF448(ISP) [CX0001]  
PIC18LF448@PLCC44 [CX2044] PIC18LF448@PLCC44(ISP) [CX0001]  
PIC18LF448@QFN44 [CX4019] PIC18LF448@TQFP44 [CX3003]  
PIC18LF448@TQFP44(ISP) [CX0001] PIC18LF4480 [CX0001]  
PIC18LF4480(ISP)(High-V) [CX0001]  
PIC18LF4480(ISP)(Low-V) [CX0001] PIC18LF4480@QFN44 [CX4018]  
PIC18LF4480@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4480@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4480@QFN44(ML) [CX4019]

PIC18LF4480@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4480@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4480@TQFP44 [CX3003]  
PIC18LF4480@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4480@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF44J10 [CX0001] PIC18LF44J10(ISP) [CX0001]  
PIC18LF44J10@QFN44 [CX4018] PIC18LF44J10@QFN44(ISP) [CX0001]  
PIC18LF44J10@QFN44(ML) [CX4019]  
PIC18LF44J10@QFN44(ML)(ISP) [CX0001]  
PIC18LF44J10@TQFP44 [CX3003]  
PIC18LF44J10@TQFP44(ISP) [CX0001]  
PIC18LF44J11 [CX0001] PIC18LF44J11(ISP) [CX0001]  
PIC18LF44J11@QFN44 [CX4018] PIC18LF44J11@QFN44(ISP) [CX0001]  
PIC18LF44J11@QFN44(ML) [CX4019]  
PIC18LF44J11@QFN44(ML)(ISP) [CX0001]  
PIC18LF44J11@TQFP44 [CX3003]  
PIC18LF44J11@TQFP44(ISP) [CX0001]  
PIC18LF44J50 [CX0001] PIC18LF44J50(ISP) [CX0001]  
PIC18LF44J50@QFN44 [CX4018] PIC18LF44J50@QFN44(ISP) [CX0001]  
PIC18LF44J50@QFN44(ML) [CX4019]  
PIC18LF44J50@QFN44(ML)(ISP) [CX0001]  
PIC18LF44J50@TQFP44 [CX3003]  
PIC18LF44J50@TQFP44(ISP) [CX0001]  
PIC18LF44K22 [CX0001] PIC18LF44K22(ISP)(H-V) [CX0001]  
PIC18LF44K22@QFN44 [CX4018]  
PIC18LF44K22@QFN44(ISP)(H-V) [CX0001]  
PIC18LF44K22@QFN44(ML) [CX4019]  
PIC18LF44K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF44K22@TQFP44 [CX3003]  
PIC18LF44K22@TQFP44(ISP)(H-V) [CX0001]  
PIC18LF44K22@UQFN40 [CX4039] PIC18LF4510 [CX0001]  
PIC18LF4510(ISP) [CX0001] PIC18LF4510@QFN44 [CX4018]  
PIC18LF4510@QFN44(ISP) [CX0001] PIC18LF4510@QFN44(ML) [CX4019]  
PIC18LF4510@QFN44(ML)(ISP) [CX0001]  
PIC18LF4510@TQFP44 [CX3003] PIC18LF4510@TQFP44(ISP) [CX0001]  
PIC18LF4515 [CX0001] PIC18LF4515(ISP)(Low-V) [CX0001]  
PIC18LF4515@QFN44 [CX4018]  
PIC18LF4515@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4515@QFN44(ML) [CX4019]  
PIC18LF4515@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4515@TQFP44 [CX3003]  
PIC18LF4515@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF452 [CX0001] PIC18LF452(ISP) [CX0001]  
PIC18LF452@PLCC44 [CX2044] PIC18LF452@PLCC44(ISP) [CX0001]  
PIC18LF452@QFN44 [CX4019] PIC18LF452@TQFP44 [CX3003]  
PIC18LF452@TQFP44(ISP) [CX0001] PIC18LF4520 [CX0001]  
PIC18LF4520(ISP) [CX0001] PIC18LF4520@QFN44 [CX4018]  
PIC18LF4520@QFN44(ISP) [CX0001] PIC18LF4520@QFN44(ML) [CX4019]  
PIC18LF4520@QFN44(ML)(ISP) [CX0001]  
PIC18LF4520@TQFP44 [CX3003] PIC18LF4520@TQFP44(ISP) [CX0001]  
PIC18LF4523 [CX0001]  
PIC18LF4523(ISP)(High-V) [CX0001]  
PIC18LF4523(ISP)(Low-V) [CX0001] PIC18LF4523@QFN44 [CX4018]  
PIC18LF4523@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4523@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4523@QFN44(ML) [CX4019]  
PIC18LF4523@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4523@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4523@TQFP44 [CX3003]

PIC18LF4523@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4523@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4525 [CX0001] PIC18LF4525(ISP)(Low-V) [CX0001]  
PIC18LF4525@QFN44 [CX4018]  
PIC18LF4525@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4525@QFN44(ML) [CX4019]  
PIC18LF4525@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4525@TQFP44 [CX3003]  
PIC18LF4525@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4539 [CX0001] PIC18LF4539(ISP) [CX0001]  
PIC18LF4539@TQFP44 [CX3003] PIC18LF4539@TQFP44(ISP) [CX0001]  
PIC18LF4550 [CX0001]  
PIC18LF4550(ISP)(High-V) [CX0001]  
PIC18LF4550(ISP)(Low-V) [CX0001] PIC18LF4550@QFN44 [CX4018]  
PIC18LF4550@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4550@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4550@QFN44(ML) [CX4019]  
PIC18LF4550@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4550@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4550@TQFP44 [CX3003]  
PIC18LF4550@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4550@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF458 [CX0001] PIC18LF458(ISP) [CX0001]  
PIC18LF458@PLCC44 [CX2044] PIC18LF458@PLCC44(ISP) [CX0001]  
PIC18LF458@QFN44 [CX4019] PIC18LF458@TQFP44 [CX3003]  
PIC18LF458@TQFP44(ISP) [CX0001] PIC18LF4580 [CX0001]  
PIC18LF4580(ISP)(High-V) [CX0001]  
PIC18LF4580(ISP)(Low-V) [CX0001] PIC18LF4580@QFN44 [CX4018]  
PIC18LF4580@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4580@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4580@QFN44(ML) [CX4019]  
PIC18LF4580@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4580@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4580@TQFP44 [CX3003]  
PIC18LF4580@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4580@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4585 [CX0001]  
PIC18LF4585(ISP)(High-V) [CX0001]  
PIC18LF4585(ISP)(Low-V) [CX0001] PIC18LF4585@QFN44 [CX4018]  
PIC18LF4585@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4585@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4585@QFN44(ML) [CX4019]  
PIC18LF4585@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4585@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4585@TQFP44 [CX3003]  
PIC18LF4585@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4585@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF45J10 [CX0001] PIC18LF45J10(ISP) [CX0001]  
PIC18LF45J10@QFN44 [CX4018] PIC18LF45J10@QFN44(ISP) [CX0001]  
PIC18LF45J10@QFN44(ML) [CX4019]  
PIC18LF45J10@QFN44(ML)(ISP) [CX0001]  
PIC18LF45J10@TQFP44 [CX3003]  
PIC18LF45J10@TQFP44(ISP) [CX0001]  
PIC18LF45J11 [CX0001] PIC18LF45J11(ISP) [CX0001]  
PIC18LF45J11@QFN44 [CX4018] PIC18LF45J11@QFN44(ISP) [CX0001]  
PIC18LF45J11@QFN44(ML) [CX4019]  
PIC18LF45J11@QFN44(ML)(ISP) [CX0001]  
PIC18LF45J11@TQFP44 [CX3003]  
PIC18LF45J11@TQFP44(ISP) [CX0001]

PIC18LF45J50 [CX0001] PIC18LF45J50(ISP) [CX0001]  
PIC18LF45J50@QFN44 [CX4018] PIC18LF45J50@QFN44(ISP) [CX0001]  
PIC18LF45J50@QFN44(ML) [CX4019]  
PIC18LF45J50@QFN44(ML)(ISP) [CX0001]  
PIC18LF45J50@TQFP44 [CX3003]  
PIC18LF45J50@TQFP44(ISP) [CX0001]  
PIC18LF45K22 [CX0001] PIC18LF45K22(ISP)(H-V) [CX0001]  
PIC18LF45K22@QFN44 [CX4018]  
PIC18LF45K22@QFN44(ISP)(H-V) [CX0001]  
PIC18LF45K22@QFN44(ML) [CX4019]  
PIC18LF45K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF45K22@TQFP44 [CX3003]  
PIC18LF45K22@TQFP44(ISP)(H-V) [CX0001]  
PIC18LF45K22@UQFN40 [CX4039] PIC18LF45K50 [CX0001]  
PIC18LF45K50@ISP [CX0001] PIC18LF45K50@QFN44 [CX4019]  
PIC18LF45K50@TQFP44 [CX3003] PIC18LF45K50@UQFN40 [CX4039]  
PIC18LF45K80 [CX0001] PIC18LF45K80(ISP) [CX0001]  
PIC18LF45K80@QFN44 [CX4019] PIC18LF45K80@QFN44(ISP) [CX0001]  
PIC18LF45K80@TQFP44 [CX3003]  
PIC18LF45K80@TQFP44(ISP) [CX0001]  
PIC18LF4610 [CX0001] PIC18LF4610(ISP)(Low-V) [CX0001]  
PIC18LF4610@QFN44 [CX4018]  
PIC18LF4610@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4610@QFN44(ML) [CX4019]  
PIC18LF4610@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4610@TQFP44 [CX3003]  
PIC18LF4610@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4620 [CX0001] PIC18LF4620(ISP)(Low-V) [CX0001]  
PIC18LF4620@QFN44 [CX4018]  
PIC18LF4620@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4620@QFN44(ML) [CX4019]  
PIC18LF4620@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4620@TQFP44 [CX3003]  
PIC18LF4620@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4680 [CX0001]  
PIC18LF4680(ISP)(High-V) [CX0001]  
PIC18LF4680(ISP)(Low-V) [CX0001] PIC18LF4680@QFN44 [CX4018]  
PIC18LF4680@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4680@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4680@QFN44(ML) [CX4019]  
PIC18LF4680@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4680@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4680@TQFP44 [CX3003]  
PIC18LF4680@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4680@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4682 [CX0001]  
PIC18LF4682(ISP)(High-V) [CX0001]  
PIC18LF4682(ISP)(Low-V) [CX0001] PIC18LF4682@QFN44 [CX4018]  
PIC18LF4682@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4682@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4682@QFN44(ML) [CX4019]  
PIC18LF4682@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4682@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4682@TQFP44 [CX3003]  
PIC18LF4682@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4682@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF4685 [CX0001]  
PIC18LF4685(ISP)(High-V) [CX0001]  
PIC18LF4685(ISP)(Low-V) [CX0001] PIC18LF4685@QFN44 [CX4018]

PIC18LF4685@QFN44(ISP)(High-V) [CX0001]  
PIC18LF4685@QFN44(ISP)(Low-V) [CX0001]  
PIC18LF4685@QFN44(ML) [CX4019]  
PIC18LF4685@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF4685@QFN44(ML)(ISP)(L-V) [CX0001]  
PIC18LF4685@TQFP44 [CX3003]  
PIC18LF4685@TQFP44(ISP)(High-V) [CX0001]  
PIC18LF4685@TQFP44(ISP)(Low-V) [CX0001]  
PIC18LF46J11 [CX0001] PIC18LF46J11(ISP) [CX0001]  
PIC18LF46J11@QFN44 [CX4018] PIC18LF46J11@QFN44(ISP) [CX0001]  
PIC18LF46J11@QFN44(ML) [CX4019]  
PIC18LF46J11@QFN44(ML)(ISP) [CX0001]  
PIC18LF46J11@TQFP44 [CX3003]  
PIC18LF46J11@TQFP44(ISP) [CX0001]  
PIC18LF46J13 [CX0001] PIC18LF46J13(ISP) [CX0001]  
PIC18LF46J13@QFN44 [CX4018] PIC18LF46J13@QFN44(ISP) [CX0001]  
PIC18LF46J13@QFN44(ML) [CX4019]  
PIC18LF46J13@QFN44(ML)(ISP) [CX0001]  
PIC18LF46J13@TQFP44 [CX3003]  
PIC18LF46J13@TQFP44(ISP) [CX0001]  
PIC18LF46J50 [CX0001] PIC18LF46J50(ISP) [CX0001]  
PIC18LF46J50@QFN44 [CX4018] PIC18LF46J50@QFN44(ISP) [CX0001]  
PIC18LF46J50@QFN44(ML) [CX4019]  
PIC18LF46J50@QFN44(ML)(ISP) [CX0001]  
PIC18LF46J50@TQFP44 [CX3003]  
PIC18LF46J50@TQFP44(ISP) [CX0001]  
PIC18LF46J53 [CX0001] PIC18LF46J53(ISP) [CX0001]  
PIC18LF46J53@QFN44 [CX4018] PIC18LF46J53@QFN44(ISP) [CX0001]  
PIC18LF46J53@QFN44(ML) [CX4019]  
PIC18LF46J53@QFN44(ML)(ISP) [CX0001]  
PIC18LF46J53@TQFP44 [CX3003]  
PIC18LF46J53@TQFP44(ISP) [CX0001]  
PIC18LF46K22 [CX0001] PIC18LF46K22(ISP)(H-V) [CX0001]  
PIC18LF46K22@QFN44 [CX4018]  
PIC18LF46K22@QFN44(ISP)(H-V) [CX0001]  
PIC18LF46K22@QFN44(ML) [CX4019]  
PIC18LF46K22@QFN44(ML)(ISP)(H-V) [CX0001]  
PIC18LF46K22@TQFP44 [CX3003]  
PIC18LF46K22@TQFP44(ISP)(H-V) [CX0001]  
PIC18LF46K22@UQFN40 [CX4039] PIC18LF46K50 [CX0001]  
PIC18LF46K50@ISP [CX0001] PIC18LF46K50@QFN44 [CX4019]  
PIC18LF46K50@TQFP44 [CX3003] PIC18LF46K50@UQFN40 [CX4039]  
PIC18LF46K80 [CX0001] PIC18LF46K80(ISP) [CX0001]  
PIC18LF46K80@QFN44 [CX4019] PIC18LF46K80@QFN44(ISP) [CX0001]  
PIC18LF46K80@TQFP44 [CX3003]  
PIC18LF46K80@TQFP44(ISP) [CX0001]  
PIC18LF47J13 [CX0001] PIC18LF47J13(ISP) [CX0001]  
PIC18LF47J13@QFN44 [CX4018] PIC18LF47J13@QFN44(ISP) [CX0001]  
PIC18LF47J13@QFN44(ML) [CX4019]  
PIC18LF47J13@QFN44(ML)(ISP) [CX0001]  
PIC18LF47J13@TQFP44 [CX3003]  
PIC18LF47J13@TQFP44(ISP) [CX0001]  
PIC18LF47J53 [CX0001] PIC18LF47J53(ISP) [CX0001]  
PIC18LF47J53@QFN44 [CX4018] PIC18LF47J53@QFN44(ISP) [CX0001]  
PIC18LF47J53@QFN44(ML) [CX4019]  
PIC18LF47J53@QFN44(ML)(ISP) [CX0001]  
PIC18LF47J53@TQFP44 [CX3003]  
PIC18LF47J53@TQFP44(ISP) [CX0001]  
PIC18LF6310@TQFP64 [CX3011] PIC18LF6310@TQFP64(ISP) [CX0001]

PIC18LF6390@TQFP64 [CX3011] PIC18LF6390@TQFP64(ISP) [CX0001]  
PIC18LF6393@TQFP64 [CX3011] PIC18LF6393@TQFP64(ISP) [CX0001]  
PIC18LF63J11@TQFP64 [CX3011]  
PIC18LF63J11@TQFP64(ISP) [CX0001]  
PIC18LF63J90@TQFP64 [CX3011]  
PIC18LF63J90@TQFP64(ISP) [CX0001]  
PIC18LF6410@TQFP64 [CX3011] PIC18LF6410@TQFP64(ISP) [CX0001]  
PIC18LF6490@TQFP64 [CX3011] PIC18LF6490@TQFP64(ISP) [CX0001]  
PIC18LF6493@TQFP64 [CX3011] PIC18LF6493@TQFP64(ISP) [CX0001]  
PIC18LF64J11@TQFP64 [CX3011]  
PIC18LF64J11@TQFP64(ISP) [CX0001]  
PIC18LF64J90@TQFP64 [CX3011]  
PIC18LF64J90@TQFP64(ISP) [CX0001]  
PIC18LF6520@TQFP64 [CX3011] PIC18LF6520@TQFP64(ISP) [CX0001]  
PIC18LF6525@TQFP64 [CX3011] PIC18LF6525@TQFP64(ISP) [CX0001]  
PIC18LF6527@TQFP64 [CX3011]  
PIC18LF6527@TQFP64(ISP)(High-V) [CX0001]  
PIC18LF6527@TQFP64(ISP)(Low-V) [CX0001]  
PIC18LF6585@PLCC68 [CX2068] PIC18LF6585@PLCC68(ISP) [CX0001]  
PIC18LF6585@TQFP64 [CX3011] PIC18LF6585@TQFP64(ISP) [CX0001]  
PIC18LF65J11@TQFP64 [CX3011]  
PIC18LF65J11@TQFP64(ISP) [CX0001]  
PIC18LF65J90@TQFP64 [CX3011]  
PIC18LF65J90@TQFP64(ISP) [CX0001]  
PIC18LF65K80@QFN64 [CX4023] PIC18LF65K80@QFN64(ISP) [CX0001]  
PIC18LF65K80@TQFP64 [CX3011]  
PIC18LF65K80@TQFP64(ISP) [CX0001]  
PIC18LF6620@TQFP64 [CX3011] PIC18LF6620@TQFP64(ISP) [CX0001]  
PIC18LF6621@TQFP64 [CX3011] PIC18LF6621@TQFP64(ISP) [CX0001]  
PIC18LF6622@TQFP64 [CX3011]  
PIC18LF6622@TQFP64(ISP)(High-V) [CX0001]  
PIC18LF6622@TQFP64(ISP)(Low-V) [CX0001]  
PIC18LF6627@TQFP64 [CX3011]  
PIC18LF6627@TQFP64(ISP)(High-V) [CX0001]  
PIC18LF6627@TQFP64(ISP)(Low-V) [CX0001]  
PIC18LF6628@TQFP64 [CX3011]  
PIC18LF6628@TQFP64(ISP)(High-V) [CX0001]  
PIC18LF6628@TQFP64(ISP)(Low-V) [CX0001]  
PIC18LF6680@PLCC68 [CX2068] PIC18LF6680@PLCC68(ISP) [CX0001]  
PIC18LF6680@TQFP64 [CX3011] PIC18LF6680@TQFP64(ISP) [CX0001]  
PIC18LF66K80@QFN64 [CX4023] PIC18LF66K80@QFN64(ISP) [CX0001]  
PIC18LF66K80@TQFP64 [CX3011]  
PIC18LF66K80@TQFP64(ISP) [CX0001]  
PIC18LF6720@TQFP64 [CX3011] PIC18LF6720@TQFP64(ISP) [CX0001]  
PIC18LF6722@TQFP64 [CX3011]  
PIC18LF6722@TQFP64(ISP)(High-V) [CX0001]  
PIC18LF6722@TQFP64(ISP)(Low-V) [CX0001]  
PIC18LF6723@TQFP64 [CX3011]  
PIC18LF6723@TQFP64(ISP)(High-V) [CX0001]  
PIC18LF6723@TQFP64(ISP)(Low-V) [CX0001]  
PIC18LF8310@TQFP80 [CX3016] PIC18LF8310@TQFP80(ISP) [CX0001]  
PIC18LF8390@TQFP80 [CX3016] PIC18LF8390@TQFP80(ISP) [CX0001]  
PIC18LF8393@TQFP80 [CX3016] PIC18LF8393@TQFP80(ISP) [CX0001]  
PIC18LF83J11@TQFP80 [CX3016]  
PIC18LF83J11@TQFP80(ISP) [CX0001]  
PIC18LF83J90@TQFP80 [CX3016]  
PIC18LF83J90@TQFP80(ISP) [CX0001]  
PIC18LF8410@TQFP80 [CX3016] PIC18LF8410@TQFP80(ISP) [CX0001]  
PIC18LF8490@TQFP80 [CX3016] PIC18LF8490@TQFP80(ISP) [CX0001]

PIC18LF8493@TQFP80 [CX3016] PIC18LF8493@TQFP80(ISP) [CX0001]  
PIC18LF84J11@TQFP80 [CX3016]  
PIC18LF84J11@TQFP80(ISP) [CX0001]  
PIC18LF84J90@TQFP80 [CX3016]  
PIC18LF84J90@TQFP80(ISP) [CX0001]  
PIC18LF8520@TQFP80 [CX3016] PIC18LF8520@TQFP80(ISP) [CX0001]  
PIC18LF8525@TQFP80 [CX3016] PIC18LF8525@TQFP80(ISP) [CX0001]  
PIC18LF8527@TQFP80 [CX3016]  
PIC18LF8527@TQFP80(ISP)(High-V) [CX0001]  
PIC18LF8527@TQFP80(ISP)(Low-V) [CX0001]  
PIC18LF8585@TQFP80 [CX3016] PIC18LF8585@TQFP80(ISP) [CX0001]  
PIC18LF85J11@TQFP80 [CX3016]  
PIC18LF85J11@TQFP80(ISP) [CX0001]  
PIC18LF85J90@TQFP80 [CX3016]  
PIC18LF85J90@TQFP80(ISP) [CX0001]  
PIC18LF8620@TQFP80 [CX3016] PIC18LF8620@TQFP80(ISP) [CX0001]  
PIC18LF8621@TQFP80 [CX3016] PIC18LF8621@TQFP80(ISP) [CX0001]  
PIC18LF8622@TQFP80 [CX3016]  
PIC18LF8622@TQFP80(ISP)(High-V) [CX0001]  
PIC18LF8622@TQFP80(ISP)(Low-V) [CX0001]  
PIC18LF8627@TQFP80 [CX3016]  
PIC18LF8627@TQFP80(ISP)(High-V) [CX0001]  
PIC18LF8627@TQFP80(ISP)(Low-V) [CX0001]  
PIC18LF8628@TQFP80 [CX3016]  
PIC18LF8628@TQFP80(ISP)(High-V) [CX0001]  
PIC18LF8628@TQFP80(ISP)(Low-V) [CX0001]  
PIC18LF8680@TQFP80 [CX3016] PIC18LF8680@TQFP80(ISP) [CX0001]  
PIC18LF8720@TQFP80 [CX3016] PIC18LF8720@TQFP80(ISP) [CX0001]  
PIC18LF8722@TQFP80 [CX3016]  
PIC18LF8722@TQFP80(ISP)(High-V) [CX0001]  
PIC18LF8722@TQFP80(ISP)(Low-V) [CX0001]  
PIC18LF8723@TQFP80 [CX3016]  
PIC18LF8723@TQFP80(ISP)(High-V) [CX0001]  
PIC18LF8723@TQFP80(ISP)(Low-V) [CX0001]  
PIC24EP128GP202 [CX0001] PIC24EP128GP202(ISP) [CX0001]  
PIC24EP128GP202@QFN28 [CX4014] PIC24EP128GP202@SOIC28 [CX1033]  
PIC24EP128GP202@SSOP28 [CX1026] PIC24EP128GP203(ISP) [CX0001]  
PIC24EP128GP203@VTLA36 [CX4077] PIC24EP128GP204(ISP) [CX0001]  
PIC24EP128GP204@QFN44 [CX4019]  
PIC24EP128GP204@TQFP44 [CX3003#2]  
PIC24EP128GP206(ISP) [CX0001] PIC24EP128GP206@QFN64 [CX4023]  
PIC24EP128GP206@TQFP64 [CX3011] PIC24EP128MC202 [CX0001]  
PIC24EP128MC202(ISP) [CX0001] PIC24EP128MC202@QFN28 [CX4014]  
PIC24EP128MC202@SOIC28 [CX1033] PIC24EP128MC202@SSOP28 [CX1026]  
PIC24EP128MC203(ISP) [CX0001] PIC24EP128MC203@VTLA36 [CX4077]  
PIC24EP128MC204(ISP) [CX0001] PIC24EP128MC204@QFN44 [CX4019]  
PIC24EP128MC204@TQFP44 [CX3003#2]  
PIC24EP128MC204@VTLA44 [CX4079] PIC24EP128MC206(ISP) [CX0001]  
PIC24EP128MC206@QFN64 [CX4023] PIC24EP128MC206@TQFP64 [CX3011]  
PIC24EP256GP202 [CX0001] PIC24EP256GP202(ISP) [CX0001]  
PIC24EP256GP202@QFN28 [CX4014] PIC24EP256GP202@SOIC28 [CX1033]  
PIC24EP256GP202@SSOP28 [CX1026] PIC24EP256GP203(ISP) [CX0001]  
PIC24EP256GP203@VTLA36 [CX4077] PIC24EP256GP204(ISP) [CX0001]  
PIC24EP256GP204@QFN44 [CX4019]  
PIC24EP256GP204@TQFP44 [CX3003#2]  
PIC24EP256GP206(ISP) [CX0001] PIC24EP256GP206@QFN64 [CX4023]  
PIC24EP256GP206@TQFP64 [CX3011] PIC24EP256MC202 [CX0001]  
PIC24EP256MC202(ISP) [CX0001] PIC24EP256MC202@QFN28 [CX4014]  
PIC24EP256MC202@SOIC28 [CX1033] PIC24EP256MC202@SSOP28 [CX1026]

PIC24EP256MC203(ISP) [CX0001]      PIC24EP256MC203@VTLA36 [CX4077]  
PIC24EP256MC204(ISP) [CX0001]      PIC24EP256MC204@QFN44 [CX4019]  
PIC24EP256MC204@TQFP44 [CX3003#2]  
PIC24EP256MC204@VTLA44 [CX4079]      PIC24EP256MC206(ISP) [CX0001]  
PIC24EP256MC206@QFN64 [CX4023]      PIC24EP256MC206@TQFP64 [CX3011]  
PIC24EP32GP202 [CX0001]      PIC24EP32GP202(ISP) [CX0001]  
PIC24EP32GP202@QFN28 [CX4014]      PIC24EP32GP202@SOIC28 [CX1033]  
PIC24EP32GP202@SSOP28 [CX1026]      PIC24EP32GP203(ISP) [CX0001]  
PIC24EP32GP203@VTLA36 [CX4077]      PIC24EP32GP204(ISP) [CX0001]  
PIC24EP32GP204@QFN44 [CX4019]      PIC24EP32GP204@TQFP44 [CX3003]  
PIC24EP32MC202 [CX0001]      PIC24EP32MC202(ISP) [CX0001]  
PIC24EP32MC202@QFN28 [CX4014]      PIC24EP32MC202@SOIC28 [CX1033]  
PIC24EP32MC202@SSOP28 [CX1026]      PIC24EP32MC203(ISP) [CX0001]  
PIC24EP32MC203@VTLA36 [CX4077]      PIC24EP32MC204(ISP) [CX0001]  
PIC24EP32MC204@QFN44 [CX4019]      PIC24EP32MC204@TQFP44 [CX3003]  
PIC24EP32MC204@VTLA44 [CX4079]      PIC24EP512GP202 [CX0001]  
PIC24EP512GP202(ISP) [CX0001]      PIC24EP512GP202@QFN28 [CX4014]  
PIC24EP512GP202@SOIC28 [CX1033]      PIC24EP512GP204(ISP) [CX0001]  
PIC24EP512GP204@QFN44 [CX4019]  
PIC24EP512GP204@TQFP44 [CX3003#2]  
PIC24EP512GP204@VTLA44 [CX4079]      PIC24EP512GP206(ISP) [CX0001]  
PIC24EP512GP206@QFN64 [CX4023]      PIC24EP512GP206@TQFP64 [CX3011]  
PIC24EP512M202@QFN28 [CX4014]      PIC24EP512MC202 [CX0001]  
PIC24EP512MC202(ISP) [CX0001]      PIC24EP512MC202@SOIC28 [CX1033]  
PIC24EP512MC204(ISP) [CX0001]      PIC24EP512MC204@QFN44 [CX4019]  
PIC24EP512MC204@TQFP44 [CX3003#2]  
PIC24EP512MC204@VTLA44 [CX4079]      PIC24EP512MC206(ISP) [CX0001]  
PIC24EP512MC206@QFN64 [CX4023]      PIC24EP512MC206@TQFP64 [CX3011]  
PIC24EP64GP202 [CX0001]      PIC24EP64GP202(ISP) [CX0001]  
PIC24EP64GP202@QFN28 [CX4014]      PIC24EP64GP202@SOIC28 [CX1033]  
PIC24EP64GP202@SSOP28 [CX1026]      PIC24EP64GP203(ISP) [CX0001]  
PIC24EP64GP203@VTLA36 [CX4077]      PIC24EP64GP204(ISP) [CX0001]  
PIC24EP64GP204@QFN44 [CX4019]      PIC24EP64GP204@TQFP44 [CX3003]  
PIC24EP64GP204@VTLA44 [CX4078]      PIC24EP64GP206(ISP) [CX0001]  
PIC24EP64GP206@QFN64 [CX4023]      PIC24EP64GP206@TQFP64 [CX3011]  
PIC24EP64MC202 [CX0001]      PIC24EP64MC202(ISP) [CX0001]  
PIC24EP64MC202@QFN28 [CX4014]      PIC24EP64MC202@SOIC28 [CX1033]  
PIC24EP64MC202@SSOP28 [CX1026]      PIC24EP64MC203(ISP) [CX0001]  
PIC24EP64MC203@VTLA36 [CX4077]      PIC24EP64MC204(ISP) [CX0001]  
PIC24EP64MC204@QFN44 [CX4019]      PIC24EP64MC204@TQFP44 [CX3003]  
PIC24EP64MC204@VTLA44 [CX4078]      PIC24EP64MC206(ISP) [CX0001]  
PIC24EP64MC206@QFN64 [CX4023]      PIC24EP64MC206@TQFP64 [CX3011]  
PIC24F04KA200 [CX0001]      PIC24F04KA200(ISP) [CX0001]  
PIC24F04KA200@SOIC14 [CX1033]      PIC24F04KA201 [CX0001]  
PIC24F04KA201(ISP) [CX0001]      PIC24F04KA201@QFN20 [CX4025]  
PIC24F04KA201@SOIC20 [CX1033]      PIC24F04KA201@SSOP20 [CX1026]  
PIC24F04KL100 [CX0001]      PIC24F04KL100(ISP) [CX0001]  
PIC24F04KL100@SOIC14 [CX1033]      PIC24F04KL101 [CX0001]  
PIC24F04KL101(ISP) [CX0001]      PIC24F04KL101@QFN20 [CX4025]  
PIC24F04KL101@SOIC20 [CX1033]      PIC24F04KL101@SSOP20 [CX1026]  
PIC24F08KA101 [CX0001]      PIC24F08KA101(ISP) [CX0001]  
PIC24F08KA101@QFN20 [CX4025]      PIC24F08KA101@SOIC20 [CX1033]  
PIC24F08KA101@SSOP20 [CX1026]      PIC24F08KA102 [CX0001]  
PIC24F08KA102(ISP) [CX0001]      PIC24F08KA102@QFN28 [CX4013]  
PIC24F08KA102@SOIC28 [CX1033]      PIC24F08KA102@SSOP28 [CX1026]  
PIC24F08KL200 [CX0001]      PIC24F08KL200(ISP) [CX0001]  
PIC24F08KL200@SOIC14 [CX1033]      PIC24F08KL201 [CX0001]  
PIC24F08KL201(ISP) [CX0001]      PIC24F08KL201@QFN20 [CX4025]  
PIC24F08KL201@SOIC20 [CX1033]      PIC24F08KL201@SSOP20 [CX1026]



PIC24F08KL301 [CX0001] PIC24F08KL301(ISP) [CX0001]  
PIC24F08KL301@QFN20 [CX4025] PIC24F08KL301@SOIC20 [CX1033]  
PIC24F08KL301@SSOP20 [CX1026] PIC24F08KL302 [CX0001]  
PIC24F08KL302(ISP) [CX0001] PIC24F08KL302(ML)@QFN28 [CX4014]  
PIC24F08KL302@QFN28 [CX4013] PIC24F08KL302@SOIC28 [CX1033]  
PIC24F08KL302@SSOP28 [CX1026] PIC24F08KL401 [CX0001]  
PIC24F08KL401(ISP) [CX0001] PIC24F08KL401@QFN20 [CX4025]  
PIC24F08KL401@SOIC20 [CX1033] PIC24F08KL401@SSOP20 [CX1026]  
PIC24F08KL402 [CX0001] PIC24F08KL402(ISP) [CX0001]  
PIC24F08KL402(ML)@QFN28 [CX4014] PIC24F08KL402@QFN28 [CX4013]  
PIC24F08KL402@SOIC28 [CX1033] PIC24F08KL402@SSOP28 [CX1026]  
PIC24F16KA101 [CX0001] PIC24F16KA101(ISP) [CX0001]  
PIC24F16KA101@QFN20 [CX4025] PIC24F16KA101@SOIC20 [CX1033]  
PIC24F16KA101@SSOP20 [CX1026] PIC24F16KA102 [CX0001]  
PIC24F16KA102(ISP) [CX0001] PIC24F16KA102@QFN28 [CX4013]  
PIC24F16KA102@SOIC28 [CX1033] PIC24F16KA102@SSOP28 [CX1026]  
PIC24F16KA301 [CX0001] PIC24F16KA301(ISP) [CX0001]  
PIC24F16KA301@QFN20 [CX4025] PIC24F16KA301@SOIC20 [CX1033]  
PIC24F16KA301@SSOP20 [CX1026] PIC24F16KA302 [CX0001]  
PIC24F16KA302(ISP) [CX0001] PIC24F16KA302@QFN28 [CX4013]  
PIC24F16KA302@SOIC28 [CX1033] PIC24F16KA302@SSOP28 [CX1026]  
PIC24F16KA304(ISP) [CX0001] PIC24F16KA304@QFN44 [CX4019]  
PIC24F16KA304@TQFP44 [CX3003] PIC24F16KA304@UQFN48 [CX4043]  
PIC24F16KL401 [CX0001] PIC24F16KL401(ISP) [CX0001]  
PIC24F16KL401@QFN20 [CX4025] PIC24F16KL401@SOIC20 [CX1033]  
PIC24F16KL401@SSOP20 [CX1026] PIC24F16KL402 [CX0001]  
PIC24F16KL402(ISP) [CX0001] PIC24F16KL402(ML)@QFN28 [CX4014]  
PIC24F16KL402@QFN28 [CX4013] PIC24F16KL402@SOIC28 [CX1033]  
PIC24F16KL402@SSOP28 [CX1026] PIC24F32KA301 [CX0001]  
PIC24F32KA301(ISP) [CX0001] PIC24F32KA301@QFN20 [CX4025]  
PIC24F32KA301@SOIC20 [CX1033] PIC24F32KA301@SSOP20 [CX1026]  
PIC24F32KA302 [CX0001] PIC24F32KA302(ISP) [CX0001]  
PIC24F32KA302@QFN28 [CX4013] PIC24F32KA302@SOIC28 [CX1033]  
PIC24F32KA302@SSOP28 [CX1026] PIC24F32KA304(ISP) [CX0001]  
PIC24F32KA304@QFN44 [CX4019] PIC24F32KA304@TQFP44 [CX3003]  
PIC24F32KA304@UQFN48 [CX4043] PIC24FJ128DA106(ISP) [CX0001]  
PIC24FJ128DA106@QFN64 [CX4023] PIC24FJ128DA106@TQFP64 [CX3011]  
PIC24FJ128DA110(ISP) [CX0001]  
PIC24FJ128DA110@TQFP100(1) [CX3021]  
PIC24FJ128DA110@TQFP100(2) [CX3071]  
PIC24FJ128DA206(ISP) [CX0001] PIC24FJ128DA206@QFN64 [CX4023]  
PIC24FJ128DA206@TQFP64 [CX3011] PIC24FJ128DA210(ISP) [CX0001]  
PIC24FJ128DA210@TQFP100(1) [CX3021]  
PIC24FJ128DA210@TQFP100(2) [CX3071]  
PIC24FJ128GA006@QFN64 [CX4023]  
PIC24FJ128GA006@QFN64(ISP) [CX0001]  
PIC24FJ128GA006@TQFP64 [CX3011]  
PIC24FJ128GA006@TQFP64(ISP) [CX0001]  
PIC24FJ128GA008@TQFP80 [CX3016]  
PIC24FJ128GA008@TQFP80(ISP) [CX0001]  
PIC24FJ128GA010@QFP100 [CX3021]  
PIC24FJ128GA010@QFP100(ISP) [CX0001]  
PIC24FJ128GA010@TQFP100 [CX3071]  
PIC24FJ128GA010@TQFP100(ISP) [CX0001]  
PIC24FJ128GA106@QFN64 [CX4023]  
PIC24FJ128GA106@QFN64(ISP) [CX0001]  
PIC24FJ128GA106@TQFP64 [CX3011]  
PIC24FJ128GA106@TQFP64(ISP) [CX0001]  
PIC24FJ128GA108@TQFP80 [CX3016]

PIC24FJ128GA108@TQFP80(ISP) [CX0001]  
PIC24FJ128GA110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ128GA110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ128GA110@TQFP100-1(ISP) [CX0001]  
PIC24FJ128GA110@TQFP100-2(ISP) [CX0001]  
PIC24FJ128GA306(ISP) [CX0001] PIC24FJ128GA306@QFN64 [CX4023]  
PIC24FJ128GA306@TQFP64 [CX3011] PIC24FJ128GA308(ISP) [CX0001]  
PIC24FJ128GA308@TQFP80 [CX3016] PIC24FJ128GA310(ISP) [CX0001]  
PIC24FJ128GA310@TQFP100(1) [CX3021]  
PIC24FJ128GA310@TQFP100(2) [CX3071]  
PIC24FJ128GB106@QFN64 [CX4023]  
PIC24FJ128GB106@QFN64(ISP) [CX0001]  
PIC24FJ128GB106@TQFP64 [CX3011]  
PIC24FJ128GB106@TQFP64(ISP) [CX0001]  
PIC24FJ128GB108@TQFP80 [CX3016]  
PIC24FJ128GB108@TQFP80(ISP) [CX0001]  
PIC24FJ128GB110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ128GB110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ128GB110@TQFP100-1(ISP) [CX0001]  
PIC24FJ128GB110@TQFP100-2(ISP) [CX0001]  
PIC24FJ128GB206(ISP) [CX0001] PIC24FJ128GB206@QFN64 [CX4023]  
PIC24FJ128GB206@TQFP64 [CX3011] PIC24FJ128GB210(ISP) [CX0001]  
PIC24FJ128GB210@TQFP100(1) [CX3021]  
PIC24FJ128GB210@TQFP100(2) [CX3071]  
PIC24FJ128GC006(ISP) [CX0001] PIC24FJ128GC006@QFN64 [CX4023]  
PIC24FJ128GC006@TQFP64 [CX3011] PIC24FJ128GC008(ISP) [CX0001]  
PIC24FJ128GC008@TQFP80 [CX3016] PIC24FJ128GC010(ISP) [CX0001]  
PIC24FJ128GC010@TQFP100(1) [CX3021]  
PIC24FJ128GC010@TQFP100(2) [CX3071]  
PIC24FJ16GA002 [CX0001] PIC24FJ16GA002(ISP) [CX0001]  
PIC24FJ16GA002@QFN28 [CX4014]  
PIC24FJ16GA002@QFN28(ISP) [CX0001]  
PIC24FJ16GA002@SOIC28 [CX1033]  
PIC24FJ16GA002@SOIC28(ISP) [CX0001]  
PIC24FJ16GA002@SSOP28 [CX1026]  
PIC24FJ16GA002@SSOP28(ISP) [CX0001]  
PIC24FJ16GA004@QFN44 [CX4019]  
PIC24FJ16GA004@QFN44(ISP) [CX0001]  
PIC24FJ16GA004@TQFP44 [CX3003]  
PIC24FJ16GA004@TQFP44(ISP) [CX0001]  
PIC24FJ192GA106@QFN64 [CX4023]  
PIC24FJ192GA106@QFN64(ISP) [CX0001]  
PIC24FJ192GA106@TQFP64 [CX3011]  
PIC24FJ192GA106@TQFP64(ISP) [CX0001]  
PIC24FJ192GA108@TQFP80 [CX3016]  
PIC24FJ192GA108@TQFP80(ISP) [CX0001]  
PIC24FJ192GA110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ192GA110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ192GA110@TQFP100-1(ISP) [CX0001]  
PIC24FJ192GA110@TQFP100-2(ISP) [CX0001]  
PIC24FJ192GB106@QFN64 [CX4023]  
PIC24FJ192GB106@QFN64(ISP) [CX0001]  
PIC24FJ192GB106@TQFP64 [CX3011]  
PIC24FJ192GB106@TQFP64(ISP) [CX0001]  
PIC24FJ192GB108@TQFP80 [CX3016]  
PIC24FJ192GB108@TQFP80(ISP) [CX0001]  
PIC24FJ192GB110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ192GB110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ192GB110@TQFP100-1(ISP) [CX0001]

PIC24FJ192GB110@TQFP100-2(ISP) [CX0001]  
PIC24FJ256DA106(ISP) [CX0001] PIC24FJ256DA106@QFN64 [CX4023]  
PIC24FJ256DA106@TQFP64 [CX3011] PIC24FJ256DA110(ISP) [CX0001]  
PIC24FJ256DA110@TQFP100(1) [CX3021]  
PIC24FJ256DA110@TQFP100(2) [CX3071]  
PIC24FJ256DA206(ISP) [CX0001] PIC24FJ256DA206@QFN64 [CX4023]  
PIC24FJ256DA206@TQFP64 [CX3011] PIC24FJ256DA210(ISP) [CX0001]  
PIC24FJ256DA210@TQFP100(1) [CX3021]  
PIC24FJ256DA210@TQFP100(2) [CX3071]  
PIC24FJ256GA106@QFN64 [CX4023]  
PIC24FJ256GA106@QFN64(ISP) [CX0001]  
PIC24FJ256GA106@TQFP64 [CX3011]  
PIC24FJ256GA106@TQFP64(ISP) [CX0001]  
PIC24FJ256GA108@TQFP80 [CX3016]  
PIC24FJ256GA108@TQFP80(ISP) [CX0001]  
PIC24FJ256GA110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ256GA110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ256GA110@TQFP100-1(ISP) [CX0001]  
PIC24FJ256GA110@TQFP100-2(ISP) [CX0001]  
PIC24FJ256GB106@QFN64 [CX4023]  
PIC24FJ256GB106@QFN64(ISP) [CX0001]  
PIC24FJ256GB106@TQFP64 [CX3011]  
PIC24FJ256GB106@TQFP64(ISP) [CX0001]  
PIC24FJ256GB108@TQFP80 [CX3016]  
PIC24FJ256GB108@TQFP80(ISP) [CX0001]  
PIC24FJ256GB110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ256GB110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ256GB110@TQFP100-1(ISP) [CX0001]  
PIC24FJ256GB110@TQFP100-2(ISP) [CX0001]  
PIC24FJ256GB206(ISP) [CX0001] PIC24FJ256GB206@QFN64 [CX4023]  
PIC24FJ256GB206@TQFP64 [CX3011] PIC24FJ256GB210(ISP) [CX0001]  
PIC24FJ256GB210@TQFP100(1) [CX3021]  
PIC24FJ256GB210@TQFP100(2) [CX3071]  
PIC24FJ32GA002 [CX0001] PIC24FJ32GA002(ISP) [CX0001]  
PIC24FJ32GA002@QFN28 [CX4014]  
PIC24FJ32GA002@QFN28(ISP) [CX0001]  
PIC24FJ32GA002@SOIC28 [CX1033]  
PIC24FJ32GA002@SOIC28(ISP) [CX0001]  
PIC24FJ32GA002@SSOP28 [CX1026]  
PIC24FJ32GA002@SSOP28(ISP) [CX0001]  
PIC24FJ32GA004@QFN44 [CX4019]  
PIC24FJ32GA004@QFN44(ISP) [CX0001]  
PIC24FJ32GA004@TQFP44 [CX3003]  
PIC24FJ32GA004@TQFP44(ISP) [CX0001]  
PIC24FJ32GA102 [CX0001] PIC24FJ32GA102(ISP) [CX0001]  
PIC24FJ32GA102@QFN28 [CX4014]  
PIC24FJ32GA102@QFN28(ISP) [CX0001]  
PIC24FJ32GA102@SOIC28 [CX1033]  
PIC24FJ32GA102@SOIC28(ISP) [CX0001]  
PIC24FJ32GA104@QFN44 [CX4019]  
PIC24FJ32GA104@QFN44(ISP) [CX0001]  
PIC24FJ32GA104@TQFP44 [CX3003]  
PIC24FJ32GA104@TQFP44(ISP) [CX0001]  
PIC24FJ32GB002 [CX0001] PIC24FJ32GB002(ISP) [CX0001]  
PIC24FJ32GB002@QFN28 [CX4014]  
PIC24FJ32GB002@QFN28(ISP) [CX0001]  
PIC24FJ32GB002@SOIC28 [CX1033]  
PIC24FJ32GB002@SOIC28(ISP) [CX0001]  
PIC24FJ32GB004@QFN44 [CX4019]

PIC24FJ32GB004@QFN44(ISP) [CX0001]  
PIC24FJ32GB004@TQFP44 [CX3003]  
PIC24FJ32GB004@TQFP44(ISP) [CX0001]  
PIC24FJ48GA002 [CX0001] PIC24FJ48GA002(ISP) [CX0001]  
PIC24FJ48GA002@QFN28 [CX4014]  
PIC24FJ48GA002@QFN28(ISP) [CX0001]  
PIC24FJ48GA002@SOIC28 [CX1033]  
PIC24FJ48GA002@SOIC28(ISP) [CX0001]  
PIC24FJ48GA002@SSOP28 [CX1026]  
PIC24FJ48GA002@SSOP28(ISP) [CX0001]  
PIC24FJ48GA004@QFN44 [CX4019]  
PIC24FJ48GA004@QFN44(ISP) [CX0001]  
PIC24FJ48GA004@TQFP44 [CX3003]  
PIC24FJ48GA004@TQFP44(ISP) [CX0001]  
PIC24FJ64GA002 [CX0001] PIC24FJ64GA002(ISP) [CX0001]  
PIC24FJ64GA002@QFN28 [CX4014]  
PIC24FJ64GA002@QFN28(ISP) [CX0001]  
PIC24FJ64GA002@SOIC28 [CX1033]  
PIC24FJ64GA002@SOIC28(ISP) [CX0001]  
PIC24FJ64GA002@SSOP28 [CX1026]  
PIC24FJ64GA002@SSOP28(ISP) [CX0001]  
PIC24FJ64GA004@QFN44 [CX4019]  
PIC24FJ64GA004@QFN44(ISP) [CX0001]  
PIC24FJ64GA004@TQFP44 [CX3003]  
PIC24FJ64GA004@TQFP44(ISP) [CX0001]  
PIC24FJ64GA006@QFN64 [CX4023]  
PIC24FJ64GA006@QFN64(ISP) [CX0001]  
PIC24FJ64GA006@TQFP64 [CX3011]  
PIC24FJ64GA006@TQFP64(ISP) [CX0001]  
PIC24FJ64GA008@TQFP80 [CX3016]  
PIC24FJ64GA008@TQFP80(ISP) [CX0001]  
PIC24FJ64GA010@QFP100 [CX3021]  
PIC24FJ64GA010@QFP100(ISP) [CX0001]  
PIC24FJ64GA010@TQFP100 [CX3071]  
PIC24FJ64GA010@TQFP100(ISP) [CX0001]  
PIC24FJ64GA102 [CX0001] PIC24FJ64GA102(ISP) [CX0001]  
PIC24FJ64GA102@QFN28 [CX4014]  
PIC24FJ64GA102@QFN28(ISP) [CX0001]  
PIC24FJ64GA102@SOIC28 [CX1033]  
PIC24FJ64GA102@SOIC28(ISP) [CX0001]  
PIC24FJ64GA104@QFN44 [CX4019]  
PIC24FJ64GA104@QFN44(ISP) [CX0001]  
PIC24FJ64GA104@TQFP44 [CX3003]  
PIC24FJ64GA104@TQFP44(ISP) [CX0001]  
PIC24FJ64GA106@QFN64 [CX4023]  
PIC24FJ64GA106@QFN64(ISP) [CX0001]  
PIC24FJ64GA106@TQFP64 [CX3011]  
PIC24FJ64GA106@TQFP64(ISP) [CX0001]  
PIC24FJ64GA108@TQFP80 [CX3016]  
PIC24FJ64GA108@TQFP80(ISP) [CX0001]  
PIC24FJ64GA110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ64GA110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ64GA110@TQFP100-1(ISP) [CX0001]  
PIC24FJ64GA110@TQFP100-2(ISP) [CX0001]  
PIC24FJ64GA306(ISP) [CX0001] PIC24FJ64GA306@QFN64 [CX4023]  
PIC24FJ64GA306@TQFP64 [CX3011] PIC24FJ64GA308(ISP) [CX0001]  
PIC24FJ64GA308@TQFP80 [CX3016] PIC24FJ64GA310(ISP) [CX0001]  
PIC24FJ64GA310@TQFP100(1) [CX3021]  
PIC24FJ64GA310@TQFP100(2) [CX3071]

PIC24FJ64GB002 [CX0001] PIC24FJ64GB002(ISP) [CX0001]  
PIC24FJ64GB002@QFN28 [CX4014]  
PIC24FJ64GB002@QFN28(ISP) [CX0001]  
PIC24FJ64GB002@SOIC28 [CX1033]  
PIC24FJ64GB002@SOIC28(ISP) [CX0001]  
PIC24FJ64GB004@QFN44 [CX4019]  
PIC24FJ64GB004@QFN44(ISP) [CX0001]  
PIC24FJ64GB004@TQFP44 [CX3003]  
PIC24FJ64GB004@TQFP44(ISP) [CX0001]  
PIC24FJ64GB106@QFN64 [CX4023]  
PIC24FJ64GB106@QFN64(ISP) [CX0001]  
PIC24FJ64GB106@TQFP64 [CX3011]  
PIC24FJ64GB106@TQFP64(ISP) [CX0001]  
PIC24FJ64GB108@TQFP80 [CX3016]  
PIC24FJ64GB108@TQFP80(ISP) [CX0001]  
PIC24FJ64GB110@TQFP100(12\*12\*1) [CX3071]  
PIC24FJ64GB110@TQFP100(14\*14\*1) [CX3021]  
PIC24FJ64GB110@TQFP100-1(ISP) [CX0001]  
PIC24FJ64GB110@TQFP100-2(ISP) [CX0001]  
PIC24FJ64GC006(ISP) [CX0001] PIC24FJ64GC006@QFN64 [CX4023]  
PIC24FJ64GC006@TQFP64 [CX3011] PIC24FJ64GC008(ISP) [CX0001]  
PIC24FJ64GC008@TQFP80 [CX3016] PIC24FJ64GC010(ISP) [CX0001]  
PIC24FJ64GC010@TQFP100(1) [CX3021]  
PIC24FJ64GC010@TQFP100(2) [CX3071]  
PIC24FJ96GA006@QFN64 [CX4023]  
PIC24FJ96GA006@QFN64(ISP) [CX0001]  
PIC24FJ96GA006@TQFP64 [CX3011]  
PIC24FJ96GA006@TQFP64(ISP) [CX0001]  
PIC24FJ96GA008@TQFP80 [CX3016]  
PIC24FJ96GA008@TQFP80(ISP) [CX0001]  
PIC24FJ96GA010@QFP100 [CX3021]  
PIC24FJ96GA010@QFP100(ISP) [CX0001]  
PIC24FJ96GA010@TQFP100 [CX3071]  
PIC24FJ96GA010@TQFP100(ISP) [CX0001]  
PIC24FV08KM101 [CX0001] PIC24FV08KM101(ISP) [CX0001]  
PIC24FV08KM101@QFN28 [CX4025] PIC24FV08KM101@SOIC28 [CX1033]  
PIC24FV08KM101@SSOP28 [CX1026] PIC24FV08KM102 [CX0001]  
PIC24FV08KM102(ISP) [CX0001]  
PIC24FV08KM102(ML)@QFN28 [CX4014]  
PIC24FV08KM102@QFN28 [CX4013] PIC24FV08KM102@SOIC28 [CX1033]  
PIC24FV08KM102@SSOP28 [CX1026] PIC24FV08KM202 [CX0001]  
PIC24FV08KM202(ISP) [CX0001]  
PIC24FV08KM202(ML)@QFN28 [CX4014]  
PIC24FV08KM202@QFN28 [CX4013] PIC24FV08KM202@SOIC28 [CX1033]  
PIC24FV08KM202@SSOP28 [CX1026] PIC24FV08KM204(ISP) [CX0001]  
PIC24FV08KM204@QFN44 [CX4019] PIC24FV08KM204@QFN48 [CX4043]  
PIC24FV08KM204@TQFP44 [CX3003] PIC24FV16KA301 [CX0001]  
PIC24FV16KA301(ISP) [CX0001] PIC24FV16KA301@QFN20 [CX4025]  
PIC24FV16KA301@SOIC20 [CX1033] PIC24FV16KA301@SSOP20 [CX1026]  
PIC24FV16KA302 [CX0001] PIC24FV16KA302(ISP) [CX0001]  
PIC24FV16KA302@QFN28 [CX4013] PIC24FV16KA302@QFN44 [CX4019]  
PIC24FV16KA302@SOIC28 [CX1033] PIC24FV16KA302@SSOP28 [CX1026]  
PIC24FV16KA302@TQFP44 [CX3003] PIC24FV16KA302@UQFN48 [CX4043]  
PIC24FV16KA304(ISP) [CX0001] PIC24FV16KM102 [CX0001]  
PIC24FV16KM102(ISP) [CX0001]  
PIC24FV16KM102(ML)@QFN28 [CX4014]  
PIC24FV16KM102@QFN28 [CX4013] PIC24FV16KM102@SOIC28 [CX1033]  
PIC24FV16KM102@SSOP28 [CX1026] PIC24FV16KM104(ISP) [CX0001]  
PIC24FV16KM104@QFN44 [CX4019] PIC24FV16KM104@QFN48 [CX4043]

PIC24FV16KM104@TQFP44 [CX3003]            PIC24FV16KM202 [CX0001]  
PIC24FV16KM202(ISP) [CX0001]  
PIC24FV16KM202(ML)@QFN28 [CX4014]  
PIC24FV16KM202@QFN28 [CX4013]            PIC24FV16KM202@SOIC28 [CX1033]  
PIC24FV16KM202@SSOP28 [CX1026]           PIC24FV16KM204(ISP) [CX0001]  
PIC24FV16KM204@QFN44 [CX4019]           PIC24FV16KM204@QFN48 [CX4043]  
PIC24FV16KM204@TQFP44 [CX3003]           PIC24FV32KA301 [CX0001]  
PIC24FV32KA301(ISP) [CX0001]            PIC24FV32KA301@QFN20 [CX4025]  
PIC24FV32KA301@SOIC20 [CX1033]           PIC24FV32KA301@SSOP20 [CX1026]  
PIC24FV32KA302 [CX0001]                PIC24FV32KA302(ISP) [CX0001]  
PIC24FV32KA302@QFN28 [CX4013]           PIC24FV32KA302@QFN44 [CX4019]  
PIC24FV32KA302@SOIC28 [CX1033]           PIC24FV32KA302@SSOP28 [CX1026]  
PIC24FV32KA302@TQFP44 [CX3003]           PIC24FV32KA302@UQFN48 [CX4043]  
PIC24FV32KA304(ISP) [CX0001]            PIC24HJ128GP202 [CX0001]  
PIC24HJ128GP202(ISP) [CX0001]           PIC24HJ128GP202@QFN28 [CX4032]  
PIC24HJ128GP202@SOIC28 [CX1033]           PIC24HJ128GP202@SSOP28 [CX1026]  
PIC24HJ128GP204(ISP) [CX0001]           PIC24HJ128GP204@QFN44 [CX4019]  
PIC24HJ128GP204@TQFP44 [CX3003]           PIC24HJ128GP206(ISP) [CX0001]  
PIC24HJ128GP206@QFN64 [CX4023]           PIC24HJ128GP206@TQFP64 [CX3011]  
PIC24HJ128GP206A(ISP) [CX0001]           PIC24HJ128GP206A@QFN64 [CX4023]  
PIC24HJ128GP206A@TQFP64 [CX3011]        PIC24HJ128GP210(ISP) [CX0001]  
PIC24HJ128GP210@TQFP100(1) [CX3021]  
PIC24HJ128GP210@TQFP100(2) [CX3071]  
PIC24HJ128GP210A(ISP) [CX0001]  
PIC24HJ128GP210A@TQFP100(1) [CX3021]  
PIC24HJ128GP210A@TQFP100(2) [CX3071]  
PIC24HJ128GP306(ISP) [CX0001]            PIC24HJ128GP306@QFN64 [CX4023]  
PIC24HJ128GP306@TQFP64 [CX3011]           PIC24HJ128GP306A(ISP) [CX0001]  
PIC24HJ128GP306A@QFN64 [CX4023]           PIC24HJ128GP306A@TQFP64 [CX3011]  
PIC24HJ128GP310(ISP) [CX0001]  
PIC24HJ128GP310@TQFP100(1) [CX3021]  
PIC24HJ128GP310@TQFP100(2) [CX3071]  
PIC24HJ128GP310A(ISP) [CX0001]  
PIC24HJ128GP310A@TQFP100(1) [CX3021]  
PIC24HJ128GP310A@TQFP100(2) [CX3071]  
PIC24HJ128GP502 [CX0001]                PIC24HJ128GP502(ISP) [CX0001]  
PIC24HJ128GP502@QFN28 [CX4032]           PIC24HJ128GP502@SOIC28 [CX1033]  
PIC24HJ128GP502@SSOP28 [CX1026]           PIC24HJ128GP504(ISP) [CX0001]  
PIC24HJ128GP504@QFN44 [CX4019]           PIC24HJ128GP504@TQFP44 [CX3003]  
PIC24HJ128GP504@TQFP44(DELTA) [CX3003]  
PIC24HJ128GP506(ISP) [CX0001]           PIC24HJ128GP506@QFN64 [CX4023]  
PIC24HJ128GP506@TQFP64 [CX3011]           PIC24HJ128GP506A(ISP) [CX0001]  
PIC24HJ128GP506A@QFN64 [CX4023]           PIC24HJ128GP506A@TQFP64 [CX3011]  
PIC24HJ128GP510(ISP) [CX0001]  
PIC24HJ128GP510@TQFP100(1) [CX3021]  
PIC24HJ128GP510@TQFP100(2) [CX3071]  
PIC24HJ128GP510A(ISP) [CX0001]  
PIC24HJ128GP510A@TQFP100(1) [CX3021]  
PIC24HJ128GP510A@TQFP100(2) [CX3071]  
PIC24HJ12GP201 [CX0001]                PIC24HJ12GP201(ISP) [CX0001]  
PIC24HJ12GP201@SOIC18 [CX1033]  
PIC24HJ12GP201@SOIC18(ISP) [CX0001]  
PIC24HJ12GP202 [CX0001]                PIC24HJ12GP202(ISP) [CX0001]  
PIC24HJ12GP202@QFN28 [CX4014]  
PIC24HJ12GP202@QFN28(ISP) [CX0001]  
PIC24HJ12GP202@SOIC28 [CX1033]  
PIC24HJ12GP202@SOIC28(ISP) [CX0001]  
PIC24HJ12GP202@SSOP28 [CX1026]  
PIC24HJ12GP202@SSOP28(ISP) [CX0001]

PIC24HJ16GP304@QFN44 [CX4019]  
PIC24HJ16GP304@QFN44(ISP) [CX0001]  
PIC24HJ16GP304@TQFP44 [CX3003]  
PIC24HJ16GP304@TQFP44(ISP) [CX0001]  
PIC24HJ256GP206(ISP) [CX0001] PIC24HJ256GP206@QFN64 [CX4023]  
PIC24HJ256GP206@TQFP64 [CX3011] PIC24HJ256GP206A(ISP) [CX0001]  
PIC24HJ256GP206A@QFN64 [CX4023] PIC24HJ256GP206A@TQFP64 [CX3011]  
PIC24HJ256GP210(ISP) [CX0001]  
PIC24HJ256GP210@TQFP100(1) [CX3021]  
PIC24HJ256GP210@TQFP100(2) [CX3071]  
PIC24HJ256GP210A(ISP) [CX0001]  
PIC24HJ256GP210A@TQFP100(1) [CX3021]  
PIC24HJ256GP210A@TQFP100(2) [CX3071]  
PIC24HJ256GP610(ISP) [CX0001]  
PIC24HJ256GP610@TQFP100(1) [CX3021]  
PIC24HJ256GP610@TQFP100(2) [CX3071]  
PIC24HJ256GP610A(ISP) [CX0001]  
PIC24HJ256GP610A@TQFP100(1) [CX3021]  
PIC24HJ256GP610A@TQFP100(2) [CX3071]  
PIC24HJ32GP202 [CX0001] PIC24HJ32GP202(ISP) [CX0001]  
PIC24HJ32GP202@QFN28 [CX4014]  
PIC24HJ32GP202@QFN28(ISP) [CX0001]  
PIC24HJ32GP202@SOIC28 [CX1033]  
PIC24HJ32GP202@SOIC28(ISP) [CX0001]  
PIC24HJ32GP202@SSOP28 [CX1026]  
PIC24HJ32GP202@SSOP28(ISP) [CX0001]  
PIC24HJ32GP204@QFN44 [CX4019]  
PIC24HJ32GP204@QFN44(ISP) [CX0001]  
PIC24HJ32GP204@TQFP44 [CX3003]  
PIC24HJ32GP204@TQFP44(ISP) [CX0001]  
PIC24HJ32GP302 [CX0001] PIC24HJ32GP302(ISP) [CX0001]  
PIC24HJ32GP302@QFN28 [CX4014]  
PIC24HJ32GP302@QFN28(ISP) [CX0001]  
PIC24HJ32GP302@SOIC28 [CX1033]  
PIC24HJ32GP302@SOIC28(ISP) [CX0001]  
PIC24HJ32GP302@SSOP28 [CX1026]  
PIC24HJ32GP302@SSOP28(ISP) [CX0001]  
PIC24HJ32GP304@QFN44 [CX4019]  
PIC24HJ32GP304@QFN44(ISP) [CX0001]  
PIC24HJ32GP304@TQFP44 [CX3003]  
PIC24HJ32GP304@TQFP44(ISP) [CX0001]  
PIC24HJ64GP202 [CX0001] PIC24HJ64GP202(ISP) [CX0001]  
PIC24HJ64GP202@QFN28 [CX4014]  
PIC24HJ64GP202@QFN28(ISP) [CX0001]  
PIC24HJ64GP202@SOIC28 [CX1033]  
PIC24HJ64GP202@SOIC28(ISP) [CX0001]  
PIC24HJ64GP202@SSOP28 [CX1026]  
PIC24HJ64GP202@SSOP28(ISP) [CX0001]  
PIC24HJ64GP204@QFN44 [CX4019]  
PIC24HJ64GP204@QFN44(ISP) [CX0001]  
PIC24HJ64GP204@TQFP44 [CX3003]  
PIC24HJ64GP204@TQFP44(ISP) [CX0001]  
PIC24HJ64GP206@QFN64 [CX4023]  
PIC24HJ64GP206@QFN64(ISP) [CX0001]  
PIC24HJ64GP206@TQFP64 [CX3011]  
PIC24HJ64GP206@TQFP64(ISP) [CX0001]  
PIC24HJ64GP206A@QFN64 [CX4023]  
PIC24HJ64GP206A@QFN64(ISP) [CX0001]  
PIC24HJ64GP206A@TQFP64 [CX3011]

PIC24HJ64GP206A@TQFP64(ISP) [CX0001]  
PIC24HJ64GP210@TQFP100(1)(ISP) [CX0001]  
PIC24HJ64GP210@TQFP100(12\*12\*1) [CX3071]  
PIC24HJ64GP210@TQFP100(14\*14\*1) [CX3021]  
PIC24HJ64GP210@TQFP100(2)(ISP) [CX0001]  
PIC24HJ64GP210A@TQFP100(1)(ISP) [CX0001]  
PIC24HJ64GP210A@TQFP100(12\*12\*1) [CX3071]  
PIC24HJ64GP210A@TQFP100(14\*14\*1) [CX3021]  
PIC24HJ64GP210A@TQFP100(2)(ISP) [CX0001]  
PIC24HJ64GP502 [CX0001] PIC24HJ64GP502(ISP) [CX0001]  
PIC24HJ64GP502@QFN28 [CX4014]  
PIC24HJ64GP502@QFN28(ISP) [CX0001]  
PIC24HJ64GP502@SOIC28 [CX1033]  
PIC24HJ64GP502@SOIC28(ISP) [CX0001]  
PIC24HJ64GP502@SSOP28 [CX1026]  
PIC24HJ64GP502@SSOP28(ISP) [CX0001]  
PIC24HJ64GP504@QFN44 [CX4019]  
PIC24HJ64GP504@QFN44(ISP) [CX0001]  
PIC24HJ64GP504@TQFP44 [CX3003]  
PIC24HJ64GP504@TQFP44(ISP) [CX0001]  
PIC24HJ64GP506@QFN64 [CX4023]  
PIC24HJ64GP506@QFN64(ISP) [CX0001]  
PIC24HJ64GP506@TQFP64 [CX3011]  
PIC24HJ64GP506@TQFP64(ISP) [CX0001]  
PIC24HJ64GP506A@QFN64 [CX4023]  
PIC24HJ64GP506A@QFN64(ISP) [CX0001]  
PIC24HJ64GP506A@TQFP64 [CX3011]  
PIC24HJ64GP506A@TQFP64(ISP) [CX0001]  
PIC24HJ64GP510@TQFP100(1)(ISP) [CX0001]  
PIC24HJ64GP510@TQFP100(12\*12\*1) [CX3071]  
PIC24HJ64GP510@TQFP100(14\*14\*1) [CX3021]  
PIC24HJ64GP510@TQFP100(2)(ISP) [CX0001]  
PIC24HJ64GP510A@TQFP100(1)(ISP) [CX0001]  
PIC24HJ64GP510A@TQFP100(12\*12\*1) [CX3071]  
PIC24HJ64GP510A@TQFP100(14\*14\*1) [CX3021]  
PIC24HJ64GP510A@TQFP100(2)(ISP) [CX0001]  
PIC30F2010@QFN28 [CX4014] PIC32MX340F256H@QFN64 [CX4023#1]  
PIC32MX340F256H@TQFP64 [CX3011#2]  
PIC32MX340F512H@QFN64 [CX4023#1]  
PIC32MX340F512H@TQFP64 [CX3011#2]  
PIC32MX350F256H@QFN64 [CX4023#1]  
PIC32MX350F256H@TQFP64 [CX3011#2]  
PIC32MX350F256L@QFN64 [CX4023#1]  
PIC32MX350F256L@TQFP64 [CX3011#2]  
PIC32MX360F256L@QFN64 [CX4023#1]  
PIC32MX360F256L@TQFP64 [CX3011#2]  
PIC32MX360F512H@QFN64 [CX4023#1]  
PIC32MX360F512H@TQFP64 [CX3011#2]  
PIC32MX360F512L@QFN64 [CX4023#1]  
PIC32MX360F512L@TQFP64 [CX3011#2]  
PIC32MX370F512H@QFN64 [CX4023#1]  
PIC32MX370F512H@TQFP64 [CX3011#2]  
PIC32MX370F512L@QFN64 [CX4023#1]  
PIC32MX370F512L@TQFP64 [CX3011#2]  
PIC32MX440F256H@QFN64 [CX4023#1]  
PIC32MX440F256H@TQFP64 [CX3011#2]  
PIC32MX440F512H@QFN64 [CX4023#1]  
PIC32MX440F512H@TQFP64 [CX3011#2]  
PIC32MX450F256H@QFN64 [CX4023#1]



PIC32MX450F256H@TQFP64 [CX3011#2]  
PIC32MX450F256L@QFN64 [CX4023#1]  
PIC32MX450F256L@TQFP64 [CX3011#2]  
PIC32MX460F256L@QFN64 [CX4023#1]  
PIC32MX460F256L@TQFP64 [CX3011#2]  
PIC32MX460F512L@QFN64 [CX4023#1]  
PIC32MX460F512L@TQFP64 [CX3011#2]  
PIC32MX470F512H@QFN64 [CX4023#1]  
PIC32MX470F512H@TQFP64 [CX3011#2]  
PIC32MX470F512L@QFN64 [CX4023#1]  
PIC32MX470F512L@TQFP64 [CX3011#2]  
PIC32MX575F256H@QFN64 [CX4023#1]  
PIC32MX575F256H@TQFP64 [CX3011#2]  
PIC32MX575F256L@QFN64 [CX4023#1]  
PIC32MX575F256L@TQFP64 [CX3011#2]  
PIC32MX575F512H@QFN64 [CX4023#1]  
PIC32MX575F512H@TQFP64 [CX3011#2]  
PIC32MX575F512L@QFN64 [CX4023#1]  
PIC32MX575F512L@TQFP64 [CX3011#2]  
PIC32MX675F256H@QFN64 [CX4023#1]  
PIC32MX675F256H@TQFP64 [CX3011#2]  
PIC32MX675F256L@QFN64 [CX4023#1]  
PIC32MX675F256L@TQFP64 [CX3011#2]  
PIC32MX675F512H@QFN64 [CX4023#1]  
PIC32MX675F512H@TQFP64 [CX3011#2]  
PIC32MX675F512L@QFN64 [CX4023#1]  
PIC32MX675F512L@TQFP64 [CX3011#2]  
PIC32MX695F512H@QFN64 [CX4023#1]  
PIC32MX695F512H@TQFP64 [CX3011#2]  
PIC32MX695F512L@QFN64 [CX4023#1]  
PIC32MX695F512L@TQFP64 [CX3011#2]  
PIC32MX775F256H@QFN64 [CX4023#1]  
PIC32MX775F256H@TQFP64 [CX3011#2]  
PIC32MX775F256L@QFN64 [CX4023#1]  
PIC32MX775F256L@TQFP64 [CX3011#2]  
PIC32MX775F512H@QFN64 [CX4023#1]  
PIC32MX775F512H@TQFP64 [CX3011#2]  
PIC32MX775F512L@QFN64 [CX4023#1]  
PIC32MX775F512L@TQFP64 [CX3011#2]  
PIC32MX795F512H@QFN64 [CX4023#1]  
PIC32MX795F512H@TQFP64 [CX3011#2]  
PIC32MX795F512L@QFN64 [CX4023#1]  
PIC32MX795F512L@TQFP64 [CX3011#2]  
PS200 [CX0001]  
PS200@SOIC20 [CX1033]  
PS200@SSOP20 [CX1026]  
rfPIC12C509AF@SSOP20 [CX1026]  
rfPIC12C509AF@SSOP20(ISP) [CX0001]  
rfPIC12C509AG@SOIC18 [CX1033]  
rfPIC12C509AG@SOIC18(ISP) [CX0001]  
rfPIC12LC509AF@SSOP20 [CX1026]  
rfPIC12LC509AF@SSOP20(ISP) [CX0001]  
rfPIC12LC509AG@SOIC18 [CX1033]  
rfPIC12LC509AG@SOIC18(ISP) [CX0001]

PS200(ISP) [CX0001]  
PS200@SOIC20(ISP) [CX0001]  
PS200@SSOP20(ISP) [CX0001]

## MICROCHIP(SST)

[E\(E\) PROM/FRAM/NVRAM](#)

SST25LF010@SOIC8(4.0) [CX1045]  
SST25LF010@WSON8 [CX4005]  
SST25LF010A@SOIC8(5.4) [CX1044]  
SST25LF016A@SOIC8(4.0) [CX1045#1]  
SST25LF016A@SOIC8(5.4) [CX1044#1]  
SST25LF016A@WSON8 [CX4005#1]  
SST25LF016B@SOIC8(4.0) [CX1045#1]  
SST25LF016B@SOIC8(5.4) [CX1044#1]  
SST25LF016B@WSON8 [CX4005#1]  
SST25LF020@SOIC8(5.4) [CX1044]  
SST25LF020A@SOIC8(4.0) [CX1045]  
SST25LF020A@WSON8 [CX4005]  
SST25LF040@SOIC8(5.4) [CX1044]  
SST25LF040A@SOIC8(4.0) [CX1045]  
SST25LF040A@WSON8 [CX4005]  
SST25LF080@SOIC8(5.4) [CX1044]  
SST25LF080A@SOIC8(4.0) [CX1045]  
SST25LF080A@WSON8 [CX4005]  
SST25VF010@SOIC8(5.4) [CX1044]  
SST25VF010A@SOIC8(4.0) [CX1045]  
SST25VF010A@WSON8 [CX4005]  
SST25VF016B@SOIC8(4.0) [CX1045#1]  
SST25VF016B@SOIC8(5.4) [CX1044#1]  
SST25VF016B@WSON8 [CX4005#1]  
SST25VF020@SOIC8(5.4) [CX1044]  
SST25VF020B@SOIC8(4.0) [CX1045#1]  
SST25VF020B@SOIC8(5.4) [CX1044#1]  
SST25VF020B@WSON8 [CX4005#1]  
SST25VF032B@SOIC8(4.0) [CX1045#1]  
SST25VF032B@SOIC8(5.4) [CX1044#1]  
SST25VF032B@WSON8 [CX4005#1]  
SST25VF040@SOIC8(5.4) [CX1044]  
SST25VF040B@SOIC8(4.0) [CX1045#1]  
SST25VF040B@SOIC8(5.4) [CX1044#1]  
SST25VF040B@WSON8 [CX4005#1]  
SST25VF064C@SOIC8 [CX1044#1]  
SST25VF080@SOIC8(4.0) [CX1045]  
SST25VF080@WSON8 [CX4005]  
SST25VF080B@SOIC8(4.0) [CX1045#1]  
SST25VF080B@SOIC8(5.4) [CX1044#1]  
SST25VF080B@WSON8 [CX4005#1]  
SST25VF512@SOIC8(5.4) [CX1044]  
SST25VF512A@SOIC8(4.0) [CX1045]  
SST25VF512A@WSON8 [CX4005]  
SST25WF010@SOIC8(5.4) [CX1044]  
SST25WF020@SOIC8(4.0) [CX1045]  
SST25WF020@WSON8 [CX4005]  
SST25WF040@SOIC8(5.4) [CX1044]  
SST25WF080@SOIC8(4.0) [CX1045]  
SST25WF080@WSON8 [CX4005]  
SST25WF512@SOIC8(5.4) [CX1044]

SST25LF010@SOIC8(5.4) [CX1044]  
SST25LF010A@SOIC8(4.0) [CX1045]  
SST25LF010A@WSON8 [CX4005]

SST25LF020@SOIC8(4.0) [CX1045]  
SST25LF020@WSON8 [CX4005]  
SST25LF020A@SOIC8(5.4) [CX1044]  
SST25LF040@SOIC8(4.0) [CX1045]  
SST25LF040@WSON8 [CX4005]  
SST25LF040A@SOIC8(5.4) [CX1044]  
SST25LF080@SOIC8(4.0) [CX1045]  
SST25LF080@WSON8 [CX4005]  
SST25LF080A@SOIC8(5.4) [CX1044]  
SST25VF010@SOIC8(4.0) [CX1045]  
SST25VF010@WSON8 [CX4005]  
SST25VF010A@SOIC8(5.4) [CX1044]

SST25VF020@SOIC8(4.0) [CX1045]  
SST25VF020@WSON8 [CX4005]

SST25VF032B@SOIC16 [CX1033#1]

SST25VF040@SOIC8(4.0) [CX1045]  
SST25VF040@WSON8 [CX4005]

SST25VF064C@SOIC16 [CX1033#1]  
SST25VF064C@WSON8 [CX4006#1]  
SST25VF080@SOIC8(5.4) [CX1044]

SST25VF512@SOIC8(4.0) [CX1045]  
SST25VF512@WSON8 [CX4005]  
SST25VF512A@SOIC8(5.4) [CX1044]  
SST25WF010@SOIC8(4.0) [CX1045]  
SST25WF010@WSON8 [CX4005]  
SST25WF020@SOIC8(5.4) [CX1044]  
SST25WF040@SOIC8(4.0) [CX1045]  
SST25WF040@WSON8 [CX4005]  
SST25WF080@SOIC8(5.4) [CX1044]  
SST25WF512@SOIC8(4.0) [CX1045]  
SST25WF512@WSON8 [CX4005]

## MICRON

### E (E) PROM / FRAM / NVRAM

DT28F640J3@SSOP56 [CX0051]

M25P05-A@SO8 [CX1045#1]

M25P05-A@TSSOP8 [CX1059#3]  
M25P05-A@VFQFPN8 [CX4005#1]  
M25P10-A@UFDFPN8 [CX4002#1]  
M25P16 [CX0001]  
M25P16@SO8N [CX1045#1]  
M25P16ME@UFDFPN8 [CX4081]  
M25P16MP@VFDFPN8 [CX4005#1]  
M25P20@SO8 [CX1045#1]  
M25P32@SO16 [CX1033#1]  
M25P32@VFDFPN8 [CX4006#1]  
M25P40@DFN8 [CX4005#1]  
M25P40@SO8W [CX1044#1]  
M25P40MB@UFDFPN8 [CX4002#1]  
M25P64@SO16 [CX1033#1]  
M25P80 [CX0001]  
M25P80@SO8W [CX1044#1]  
M25P80@VFDFPN8 [CX4005#1]  
M25PE10@VFQFPN8 [CX4005#1]  
M25PE16@VFQFPN8 [CX4005#1]  
M25PE20@VFQFPN8 [CX4005#1]  
M25PE40@SO8W [CX1044#1]  
M25PE80@QFN8L [CX4005#1]  
M25PE80@SO8W [CX1044#1]  
M45PE10@SO8N [CX1045#1]  
M45PE16@SO8W [CX1044#1]  
M45PE20@SO8 [CX1045#1]  
M45PE40@SO8N [CX1045#1]  
M45PE40@VFQFPN8 [CX4005#1]  
M45PE80@SO8N [CX1045#1]  
M45PE80@VFQFPN8 [CX4005#1]  
MT28F002B1VG-T@TSOP40 [CX1006]  
MT28F002B3VG-T@TSOP40 [CX1006]  
MT28F002B5VG-T@TSOP40 [CX1006]  
MT28F002C5VG-T@TSOP40 [CX1006]  
MT28F002VG-T@TSOP40 [CX1006]  
MT28F004B1VG-T@TSOP40 [CX1006]  
MT28F004B3VG-T@TSOP40 [CX1006]  
MT28F004B5VG-T@TSOP40 [CX1006]  
MT28F004VG-T@TSOP40 [CX1006]  
MT28F008B1VG-T@TSOP40 [CX1006]  
MT28F008B3VG-T@TSOP40 [CX1006]  
MT28F008B5VG-T@TSOP40 [CX1006]  
MT28F016S5VG@TSOP40 [CX1006]  
MT28F128J3A(FW203)(I.)@FBGA64 [CX5004]  
MT28F128J3A(FW501)(I.)@FBGA64 [CX5004]  
MT28F128J3A(FW502)(M.)@FBGA64 [CX5004]  
MT28F128J3A(FW503)(M.)@FBGA64 [CX5004]  
MT28F128J3A(INTEL)@TSOP56 [CX1011]  
MT28F128J3A(MICRON)@TSOP56 [CX1011]  
MT28F200B1SGB@PSOP44 [CX1014]  
MT28F200B1WGB@TSOP48 [CX1004]  
MT28F200B3SGB@PSOP44 [CX1014]  
MT28F200B3WGB@TSOP48 [CX1004]  
MT28F200B5SGB@PSOP44 [CX1014]  
MT28F200B5WGB@TSOP48 [CX1004]  
MT28F320J3A(FW201)(I.)@FBGA64 [CX5004]  
MT28F320J3A(FW204)(M.)@FBGA64 [CX5004]  
MT28F320J3A(FW207)(I.)@FBGA64 [CX5004]  
MT28F320J3A(FW208)(M.)@FBGA64 [CX5004]  
M25P05-A@UFDFPN8 [CX4002#1]  
M25P10-A@SO8 [CX1045#1]  
M25P10-A@VFQFPN8 [CX4005#1]  
M25P16@SO16 [CX1033#1]  
M25P16@SO8W [CX1044#1]  
M25P16ME@VFDFPN8 [CX4006#1]  
M25P20@QFN8L [CX4005#1]  
M25P20@VFQFPN8 [CX4005#1]  
M25P32@SO8W [CX1044#1]  
M25P32@VFQFPN8 [CX4005#1]  
M25P40@SO8N [CX1045#1]  
M25P40@VFDFPN8 [CX4005#1]  
M25P40MC@UFDFPN8 [CX4076]  
M25P64@VDFPN8 [CX4006#1]  
M25P80@SO8N [CX1045#1]  
M25P80@UFDFPN8 [CX4076]  
M25PE10@SO8N [CX1045#1]  
M25PE16@SO8W [CX1044#1]  
M25PE20@SO8N [CX1045#1]  
M25PE40@SO8N [CX1045#1]  
M25PE40@VFQFPN8 [CX4005#1]  
M25PE80@SO8N [CX1045#1]  
M25PE80@VFQFPN8 [CX4005#1]  
M45PE10@VFQPN8 [CX4005#1]  
M45PE16@VFQFPN8 [CX4005#1]  
M45PE20@VFQFPN8 [CX4005#1]  
M45PE40@SO8W [CX1044#1]  
M45PE80@QFN8L [CX4005#1]  
M45PE80@SO8W [CX1044#1]  
MT28F002B1VG-B@TSOP40 [CX1006]  
MT28F002B3VG-B@TSOP40 [CX1006]  
MT28F002B5VG-B@TSOP40 [CX1006]  
MT28F002C1VG-T@TSOP40 [CX1006]  
MT28F002VG-B@TSOP40 [CX1006]  
MT28F004B1VG-B@TSOP40 [CX1006]  
MT28F004B3VG-B@TSOP40 [CX1006]  
MT28F004B5VG-B@TSOP40 [CX1006]  
MT28F004VG-B@TSOP40 [CX1006]  
MT28F008B1VG-B@TSOP40 [CX1006]  
MT28F008B3VG-B@TSOP40 [CX1006]  
MT28F008B5VG-B@TSOP40 [CX1006]  
MT28F016S3VG@TSOP40 [CX1006]

MT28F320J3A(INTEL)@TSOP56 [CX1011]  
MT28F320J3A(MICRON)@TSOP56 [CX1011]  
MT28F322D18FH(BET)(FW536)@FBGA58 [CX5014]  
MT28F322D18FH(BET)(FW538)@FBGA58 [CX5014]  
MT28F322D18FH(BET)(FW542)@FBGA58 [CX5014]  
MT28F322D18FH(BET)(FW556)@FBGA58 [CX5014]  
MT28F322D18FH(BET)(FW559)@FBGA58 [CX5014]  
MT28F322D18FH(TET)(FW535)@FBGA58 [CX5014]  
MT28F322D18FH(TET)(FW537)@FBGA58 [CX5014]  
MT28F322D18FH(TET)(FW543)@FBGA58 [CX5014]  
MT28F322D18FH(TET)(FW557)@FBGA58 [CX5014]  
MT28F322D18FH(TET)(FW558)@FBGA58 [CX5014]  
MT28F322D20FH(BET)(FW547)@FBGA58 [CX5014]  
MT28F322D20FH(BET)(FW549)@FBGA58 [CX5014]  
MT28F322D20FH(BET)(FW550)@FBGA58 [CX5014]  
MT28F322D20FH(BET)(FW552)@FBGA58 [CX5014]  
MT28F322D20FH(TET)(FW546)@FBGA58 [CX5014]  
MT28F322D20FH(TET)(FW548)@FBGA58 [CX5014]  
MT28F322D20FH(TET)(FW551)@FBGA58 [CX5014]  
MT28F322D20FH(TET)(FW553)@FBGA58 [CX5014]  
MT28F400B1SGB@PSOP44 [CX1014] MT28F400B1SGT@PSOP44 [CX1014]  
MT28F400B1WGB@TSOP48 [CX1004] MT28F400B1WGT@TSOP48 [CX1004]  
MT28F400B3SGB@PSOP44 [CX1014] MT28F400B3SGT@PSOP44 [CX1014]  
MT28F400B3WGB@TSOP48 [CX1004] MT28F400B3WGT@TSOP48 [CX1004]  
MT28F400B5SGB@PSOP44 [CX1014] MT28F400B5SGT@PSOP44 [CX1014]  
MT28F400B5WGB@TSOP48 [CX1004] MT28F400B5WGT@TSOP48 [CX1004]  
MT28F640J3A(FW202)(I.)@FBGA64 [CX5004]  
MT28F640J3A(FW205)(M.)@FBGA64 [CX5004]  
MT28F640J3A(FW206)(I.)@FBGA64 [CX5004]  
MT28F640J3A(FW209)(M.)@FBGA64 [CX5004]  
MT28F640J3A(FW505)(I.)@FBGA64 [CX5004]  
MT28F640J3A(FW506)(M.)@FBGA64 [CX5004]  
MT28F640J3A(INTEL)@TSOP56 [CX1011]  
MT28F640J3A(MICRON)@TSOP56 [CX1011]  
MT28F800B1SGB@PSOP44 [CX1014] MT28F800B1SGT@PSOP44 [CX1014]  
MT28F800B1WGB@TSOP48 [CX1004] MT28F800B1WGT@TSOP48 [CX1004]  
MT28F800B3SGB@PSOP44 [CX1014] MT28F800B3SGT@PSOP44 [CX1014]  
MT28F800B3WGB@TSOP48 [CX1004] MT28F800B3WGT@TSOP48 [CX1004]  
MT28F800B5SGB@PSOP44 [CX1014] MT28F800B5SGT@PSOP44 [CX1014]  
MT28F800B5WGB@TSOP48 [CX1004] MT28F800B5WGT@TSOP48 [CX1004]  
MT29F16G08ABABA@TSOP48 [CX1004-1]  
MT29F16G08CBABA@TSOP48 [CX1004-1]  
MT29F16G08CBACA@TSOP48 [CX1004-3]  
MT29F16G08FAAWC@TSOP48 [CX1004] MT29F1G08AACWP@TSOP48 [CX1004]  
MT29F1G08ABADA@TSOP48 [CX1004-3] MT29F1G08ABAEA@TSOP48 [CX1004-3]  
MT29F1G08ABAEAH4@FBGA63 [CX5046-1]  
MT29F1G08ABAWP@TSOP48 [CX1004] MT29F1G16ABAWP@TSOP48 [CX1004]  
MT29F2G08AAAWG@TSOP48 [CX1004] MT29F2G08AACWP@TSOP48 [CX1004-1]  
MT29F2G08AADWP@TSOP48 [CX1004-1] MT29F2G08ABAEA@TSOP48 [CX1004-3]  
MT29F2G08ABDWP@TSOP48 [CX1004-1] MT29F2G16AABWP@TSOP48 [CX1004]  
MT29F2G16AADWP@TSOP48 [CX1004]  
MT29F2G16ABAEAWP@TSOP48 [CX1004-1]  
MT29F32G08ABAAAWP@TSOP48 [CX1004-3]  
MT29F32G08AFACAWP(2G)@TSOP48 [CX1004-3]  
MT29F32G08CBACAWP(full)@TSOP48 [CX1004-3]  
MT29F32G08CBACAWP@TSOP48 [CX1004-3]  
MT29F4G08AAAWP@TSOP48 [CX1004] MT29F4G08AACWC@TSOP48 [CX1004-1]  
MT29F4G08AACWP@TSOP48 [CX1004-1]  
MT29F4G08ABADAWP@TSOP48 [CX1004-1]

MT29F4G08ABCWC@TSOP48 [CX1004-1] MT29F4G08BABWP@TSOP48 [CX1004]  
MT29F4G16ABADAWP@TSOP48 [CX1004-1]  
MT29F64G08CBAAAWP@TSOP48 [CX1004-1]  
MT29F8G08AAAWP@TSOP48 [CX1004-1]  
MT29F8G08ABABAWP@TSOP48 [CX1004-3]  
MT29F8G08ABACAWP@TSOP48 [CX1004-3]  
MT29F8G08MADWC@TSOP48 [CX1004-1] N25Q008A@DFN8 [CX4081]  
N25Q008A@SOP8 [CX1045#1] N25Q008A@UFDVFN8 [CX4005#1]  
N25Q008A@XFCSP8 [CX5221] N25Q00AA13G1240F [CX5157]  
N25Q00AA13G1240X [CX5157] N25Q00AA13GSF40F [CX1033#1]  
N25Q00AA13GSF40G [CX1033#1] N25Q016A11E5140F [CX5221]  
N25Q016A11ESC40F [CX1044#1] N25Q016A11ESC40G [CX1045#1]  
N25Q032A11EF640E [CX4005#1] N25Q032A11EF640F [CX4005#1]  
N25Q032A11ESE40F [CX1044#1] N25Q032A11ESE40G [CX1044#1]  
N25Q032A11ESF40F [CX1033#1] N25Q032A11ESF40G [CX1033#1]  
N25Q032A13E1240E [CX5157] N25Q032A13E1240F [CX5157]  
N25Q032A13E1241E [CX5157] N25Q032A13E1241F [CX5157]  
N25Q032A13EF440E [CX4081] N25Q032A13EF440F [CX4081]  
N25Q032A13EF640E [CX4005#1] N25Q032A13EF640F [CX4005#1]  
N25Q032A13EF840E [CX4005#1] N25Q032A13EF840F [CX4005#1]  
N25Q032A13ESC40F [CX1045#1] N25Q032A13ESC40G [CX1045#1]  
N25Q032A13ESCA0F [CX1045#1] N25Q032A13ESE40F [CX1044#1]  
N25Q032A13ESE40G [CX1044#1] N25Q032A13ESE40E [CX1044#1]  
N25Q032A13ESEH0F [CX1044#1] N25Q032A13ESF40F [CX1033#1]  
N25Q032A13ESF40G [CX1033#1] N25Q032A13ESFA0F [CX1033#1]  
N25Q032A13ESFH0F [CX1033#1] N25Q064A11EF640E [CX4006#1]  
N25Q064A11EF640F [CX4006#1] N25Q064A11ESE40F [CX1044#1]  
N25Q064A11ESE40G [CX1044#1] N25Q064A11ESF40F [CX1033#1]  
N25Q064A11ESF40G [CX1033#1] N25Q064A13E1240E [CX5157]  
N25Q064A13E1240F [CX5157] N25Q064A13E1241E [CX5157]  
N25Q064A13E1241F [CX5157] N25Q064A13E1247E [CX5157]  
N25Q064A13E1247F [CX5157] N25Q064A13EF640E [CX4006#1]  
N25Q064A13EF640F [CX4006#1] N25Q064A13EF840E [CX4006#1]  
N25Q064A13EF840F [CX4006#1] N25Q064A13EF8A0F [CX4006#1]  
N25Q064A13EF8H0F [CX4006#1] N25Q064A13ESE40E [CX1044#1]  
N25Q064A13ESE40F [CX1044#1] N25Q064A13ESE40G [CX1044#1]  
N25Q064A13ESEH0F [CX1044#1] N25Q064A13ESF40F [CX1033#1]  
N25Q064A13ESF40G [CX1033#1] N25Q064A13ESF41F [CX1033#1]  
N25Q064A13ESF41G [CX1033#1] N25Q064A13ESF42F [CX1033#1]  
N25Q064A13ESF42G [CX1033#1] N25Q064A13ESFA0F [CX1033#1]  
N25Q064A13ESFH0E [CX1033#1] N25Q064A13ESFH0F [CX1033#1]  
N25Q128@BGA24 [CX5157] N25Q128@MLP8 [CX4005#1]  
N25Q128@SOIC16 [CX1033#1] N25Q128@SOP8 [CX1044#1]  
N25Q128@VDFPN8 [CX4006#1] N25Q128A11B@BGA24 [CX5157]  
N25Q128A11B@MLP8 [CX4005#1] N25Q128A11B@SOIC16 [CX1033#1]  
N25Q128A11B@SOP8 [CX1044#1] N25Q128A11B@VDFPN8 [CX4006#1]  
N25Q128A11E@BGA24 [CX5157] N25Q128A11E@MLP8 [CX4005#1]  
N25Q128A11E@SOIC16 [CX1033#1] N25Q128A11E@SOP8 [CX1044#1]  
N25Q128A11E@VDFPN8 [CX4006#1] N25Q128A11T@BGA24 [CX5157]  
N25Q128A11T@MLP8 [CX4005#1] N25Q128A11T@SOIC16 [CX1033#1]  
N25Q128A11T@SOP8 [CX1044#1] N25Q128A11T@VDFPN8 [CX4006#1]  
N25Q128A13B@BGA24 [CX5157] N25Q128A13B@MLP8 [CX4005#1]  
N25Q128A13B@SOIC16 [CX1033#1] N25Q128A13B@SOP8 [CX1044#1]  
N25Q128A13B@VDFPN8 [CX4006#1] N25Q128A13E@BGA24 [CX5157]  
N25Q128A13E@MLP8 [CX4005#1] N25Q128A13E@SOIC16 [CX1033#1]  
N25Q128A13E@SOP8 [CX1044#1] N25Q128A13E@VDFPN8 [CX4006#1]  
N25Q128A13T@BGA24 [CX5157] N25Q128A13T@MLP8 [CX4005#1]  
N25Q128A13T@SOIC16 [CX1033#1] N25Q128A13T@SOP8 [CX1044#1]  
N25Q128A13T@VDFPN8 [CX4006#1] N25Q256A@BGA24 [CX5157]

N25Q256A@MLP8 [CX4005#1]	N25Q256A@SOIC16 [CX1033#1]
N25Q256A@SOP8 [CX1044#1]	N25Q256A@VDFN8 [CX4006#1]
N25Q256A11E1240E [CX5157]	N25Q256A11E1240F [CX5157]
N25Q256A11E1241E [CX5157]	N25Q256A11E1241F [CX5157]
N25Q256A11EF840E [CX4006#1]	N25Q256A11EF840F [CX4006#1]
N25Q256A11ESF40F [CX1033#1]	N25Q256A11ESF40G [CX1033#1]
N25Q256A13E1240E [CX5157]	N25Q256A13E1240F [CX5157]
N25Q256A13E1241E [CX5157]	N25Q256A13E1241F [CX5157]
N25Q256A13EF840E [CX4006#1]	N25Q256A13EF840F [CX4006#1]
N25Q256A13ESF40F [CX1033#1]	N25Q256A13ESF40G [CX1033#1]
N25Q256A13ESFA0F [CX1033#1]	N25Q256A13ESFH0F [CX1033#1]
N25Q256A13Ex@BGA24 [CX5157]	N25Q256A13Ex@MLP8 [CX4005#1]
N25Q256A13Ex@SOIC16 [CX1033#1]	N25Q256A13Ex@SOP8 [CX1044#1]
N25Q256A13Ex@VDFN8 [CX4006#1]	N25Q256A33E1241E [CX5157]
N25Q256A33E1241F [CX5157]	N25Q256A33EF840E [CX4006#1]
N25Q256A33EF840F [CX4006#1]	N25Q256A33ESF40F [CX1033#1]
N25Q256A33ESF40G [CX1033#1]	N25Q256A73ESF40F [CX1033#1]
N25Q256A73ESF40G [CX1033#1]	N25Q256A83E1240E [CX5157]
N25Q256A83E1240F [CX5157]	N25Q256A83E1241E [CX5157]
N25Q256A83E1241F [CX5157]	N25Q256A83ESF40F [CX1033#1]
N25Q256A83ESF40G [CX1033#1]	N25Q512A11G1240E [CX5157]
N25Q512A11G1240F [CX5157]	N25Q512A11GSF40F [CX1033#1]
N25Q512A11GSF40G [CX1033#1]	N25Q512A13G1240E [CX5157]
N25Q512A13G1240F [CX5157]	N25Q512A13G1241E [CX5157]
N25Q512A13G1241F [CX5157]	N25Q512A13GF840E [CX4006#1]
N25Q512A13GF840F [CX4006#1]	N25Q512A13GSF40F [CX1033#1]
N25Q512A13GSF40G [CX1033#1]	N25Q512A83G1240E [CX5157]
N25Q512A83G1240F [CX5157]	N25Q512A83G1241E [CX5157]
N25Q512A83G1241F [CX5157]	N25Q512A83GSF40F [CX1033#1]
N25Q512A83GSF40G [CX1033#1]	N3L0219071F5620@FBGA64 [CX5066]
N3L0219081F5620@FBGA64 [CX5066]	N3L0219091F5620@FBGA64 [CX5066]
NP5Q032AE3ESFC0E [CX1033#1]	NP5Q064AE3ESFC0E [CX1033#1]
NP5Q128A13ESFC0E [CX1033#1]	NP5Q128AE3ESFC0E [CX1033#1]

## MICRONAS

### MICROCONTROLLER

SDA555XFL@SDIP52 [CX0056]

## MICRON-CUSTOMER

### E (E) PROM/FRAM/NVRAM

MT29F32G08CBABAWP(intel)@TSOP48 [CX1004]

## MIP

### E (E) PROM/FRAM/NVRAM

M71PL064B0@FBGA56 [CX5045]

M71PL064B0@FBGA56(ZTE) [CX5005]

## MIRA

### E (E) PROM/FRAM/NVRAM

P1UAGA30AT@TSOP48 [CX1004-1]  
PSU2GA30BT@TSOP48 [CX1004-3]

PSU1GA30TH@TSOP48 [CX1004-1]  
PSU4GA30AT@TSOP48 [CX1004-3]

## MITSUBISHI

### MICROCONTROLLER

R5F21346XJFP [CX3007]  
R5F21347XJFP [CX3007]  
R5F21348XJFP [CX3007]  
R5F2134AXJFP [CX3007]  
R5F2134CXJFP [CX3007]

R5F21346XKFP [CX3007]  
R5F21347XKFP [CX3007]  
R5F21348XKFP [CX3007]  
R5F2134AXKFP [CX3007]  
R5F2134CXKFP [CX3007]

## MITSUBISHI

### E (E) PROM/FRAM/NVRAM

M5L27128K [CX0001]  
M5L27256K [CX0001]  
M5L2732A [CX0001]  
M5L27512K [CX0001]  
M5L27C512A [CX0001]  
M5M27256P [CX0001]  
M5M2764P [CX0001]  
M5M27C100K@PLCC32 [CX2032]  
M5M27C100P [CX0001]  
M5M27C100P@TSOP32 [CX1002]  
M5M27C101JK@PLCC32 [CX2032]  
M5M27C101K [CX0001]  
M5M27C101K@TSOP32 [CX1002]  
M5M27C101P@PLCC32 [CX2032]  
M5M27C102K [CX0001]  
M5M27C102P [CX0001]  
M5M27C128K [CX0001]  
M5M27C201K@PLCC32 [CX2032]  
M5M27C202K [CX0001]  
M5M27C256(K) [CX0001]  
M5M27C256A(FP) [CX0001]  
M5M27C256A(P) [CX0001]  
M5M27C401K@PLCC32 [CX2032]  
M5M27C402K [CX0001]  
M5M27C512A(FP) [CX0001]  
M5M27C512A(P) [CX0001]  
M5M28F101(REVERSE)@TSOP32 [CX1002]  
M5M28F101@PLCC32 [CX2032]  
M5M28F101@TSOP32 [CX1002]  
M5M28F101A(REVERSE)@TSOP32 [CX1002]  
M5M28F101A@PLCC32 [CX2032]  
M5M28F101A@TSOP32 [CX1002]  
M5M28FT800(VP)@TSOP48 [CX1043]  
M5M29FB800(FP)@PSOP44 [CX1014]  
M5M29FT160A@TSOP48 [CX1043]  
M5M29FT800(VP)@TSOP48 [CX1043]  
M5M29GB320(VP)@TSOP48 [CX1043]  
M5M29GB640VP@TSOP48 [CX1043]  
M5M29GT320(VP)@TSOP48 [CX1043]

M5L2716 [CX0001]  
M5L2732 [CX0001]  
M5L27512 [CX0001]  
M5L2764K [CX0001]  
M5M27128P [CX0001]  
M5M27512P [CX0001]  
M5M27C100K [CX0001]  
M5M27C100K@TSOP32 [CX1002]  
M5M27C100P@PLCC32 [CX2032]  
M5M27C101JK [CX0001]  
M5M27C101JK@TSOP32 [CX1002]  
M5M27C101K@PLCC32 [CX2032]  
M5M27C101P [CX0001]  
M5M27C101P@TSOP32 [CX1002]  
M5M27C102K@PLCC44 [CX2044]  
M5M27C102P@PLCC44 [CX2044]  
M5M27C201K [CX0001]  
M5M27C201K@TSOP32 [CX1002]  
M5M27C202K@PLCC44 [CX2044]  
M5M27C256(P) [CX0001]  
M5M27C256A(K) [CX0001]  
M5M27C401K [CX0001]  
M5M27C401K@TSOP32 [CX1002]  
M5M27C512(FP) [CX0001]  
M5M27C512A(K) [CX0001]  
M5M28F101 [CX0001]  
M5M28F101@SOP32 [CX1019]  
M5M28F101A [CX0001]  
M5M28F101A@SOIC32 [CX1019]  
M5M28FB800(VP)@TSOP48 [CX1043]  
M5M29FB160A@TSOP48 [CX1043]  
M5M29FB800(VP)@TSOP48 [CX1043]  
M5M29FT800(FP)@PSOP44 [CX1014]  
M5M29GB160B(VP)@TSOP48 [CX1043]  
M5M29GB320(WG)@CBGA48 [CX50UN]  
M5M29GT160B(VP)@TSOP48 [CX1043]  
M5M29GT320(WG)@CBGA48 [CX50UN]

M5M29GT640VP@TSOP48 [CX1043]  
M5M29JT160A@TSOP48 [CX1043]  
M6M80011A@SOIC10 [CX1032]  
M6M80021 [CX0001]  
M6M80021@SOIC16 [CX1032]  
M6M80041@SOIC10 [CX1032]  
M6MG3T641S16TP@TSOP52 [CX1009]  
M6MGB321S4TP@TSOP52 [CX1009]  
M6MGB32BS4WG@CSP66 [CX5001]  
M6MGB331S8KT@TSOP52 [CX1009]  
M6MGB641S16TP@TSOP52 [CX1009]  
M6MGB641S8TP@TSOP52 [CX1009]  
M6MGB64BS8WG@CSP67 [CX5001]  
M6MGE157S4KT@TSOP52 [CX1009]  
M6MGT321S4TP@TSOP52 [CX1009]  
M6MGT32BS4WG@CSP66 [CX5001]  
M6MGT331S8KT@TSOP52 [CX1009]  
M6MGT641S16TP@TSOP52 [CX1009]  
M6MGT641S8TP@TSOP52 [CX1009]  
M6MGT64BS8WG@CSP67 [CX5001]

M5M29JB160A@TSOP48 [CX1043]  
M6M80011A [CX0001]  
M6M80011A@SOIC16 [CX1032]  
M6M80021@SOIC10 [CX1032]  
M6M80041 [CX0001]  
M6MG3B641S16TP@TSOP52 [CX1009]  
M6MGB166S4B(WG)@FBGA72 [CX5001]  
M6MGB321S8TP@TSOP52 [CX1009]  
M6MGB32BS8WG@CSP66 [CX5001]  
M6MGB33BS8AWG@CSP66 [CX5001]  
M6MGB641S4TP@TSOP52 [CX1009]  
M6MGB64BS4WG@CSP67 [CX5001]  
M6MGD137W33(WG)@CSP72 [CX5053]  
M6MGT166S4B(WG)@FBGA72 [CX5001]  
M6MGT321S8TP@TSOP52 [CX1009]  
M6MGT32BS8WG@CSP66 [CX5001]  
M6MGT33BS8AWG@CSP66 [CX5001]  
M6MGT641S4TP@TSOP52 [CX1009]  
M6MGT64BS4WG@CSP67 [CX5001]

#### DRAM & SRAM

M5M51008BFP [CX1020]  
M5M51008DFP [CX1020]

M5M51008BP [CX0001]  
M5M51008DP [CX0001]

#### MICROCONTROLLER

M30260F3AGP@QFP48 [CX3007]  
M30260F3VGP@QFP48 [CX3007]  
M30260F6TGP@QFP48 [CX3007]  
M30260F8AGP@QFP48 [CX3007]  
M30260F8VGP@QFP48 [CX3007]  
M30262F4GP@QFP48 [CX3007]  
M30262F8GP@QFP48 [CX3007]  
M30263F6AFP@SSOP42 [CX1056]  
M30620FCAFP@PQFP100 [CX3022]  
M30620FCNFP@PQFP100 [CX3022]  
M30620FCFP@PQFP100 [CX3022]  
M30620FCPGP@TQFP100 [CX3021]  
M30621FCPGP@TQFP100(S) [CX3018]  
M30622F8PFP@PQFP100(S) [CX3022]  
M30622F8PGP@TQFP100(S) [CX3021]  
M30624FGAGP@TQFP100 [CX3021]  
M30624FGMGP@TQFP100 [CX3021]  
M30624FGNGP@TQFP100 [CX3021]  
M30624FGPFP@PQFP100(S) [CX3022]  
M30624FGPGP@TQFP100(S) [CX3021]  
M30626FHPFP@PQFP100(S) [CX3022]  
M30626FHPGP@TQFP100(S) [CX3021]  
M30626FJFP@PQFP100(S) [CX3022]  
M30626FJPGP@PQFP100(S) [CX3021]  
M3062AFCTFP@PQFP100(S) [CX3022]  
M3062AFCTGP@PQFP100(S) [CX3021]  
M3062AFCVFP@PQFP100(S) [CX3022]  
M3062AFCVGP@PQFP100(S) [CX3021]  
M3062CF8TFP@PQFP100(S) [CX3022]  
M3062CF8TGP@PQFP100(S) [CX3021]

M30260F3TGP@QFP48 [CX3007]  
M30260F6AGP@QFP48 [CX3007]  
M30260F6VGP@QFP48 [CX3007]  
M30260F8TGP@QFP48 [CX3007]  
M30262F3GP@QFP48 [CX3007]  
M30262F6GP@QFP48 [CX3007]  
M30263F3AFP@SSOP42 [CX1056]  
M30263F8AFP@SSOP42 [CX1056]  
M30620FCAGP@TQFP100 [CX3021]  
M30620FCNGP@TQFP100 [CX3021]  
M30620FCFP@PQFP100(S) [CX3022]  
M30620FCPGP@TQFP100(S) [CX3021]  
M30622F8PFP@PQFP100 [CX3022]  
M30622F8PGP@TQFP100 [CX3021]  
M30624FGAFP@PQFP100 [CX3022]  
M30624FGMFP@PQFP100 [CX3022]  
M30624FGNFP@PQFP100 [CX3022]  
M30624FGPFP@PQFP100 [CX3022]  
M30624FGPGP@TQFP100 [CX3021]  
M30626FHPFP@PQFP100 [CX3022]  
M30626FHPGP@TQFP100 [CX3021]  
M30626FJFP@PQFP100 [CX3022]  
M30626FJPGP@PQFP100 [CX3021]  
M3062AFCTFP@PQFP100 [CX3022]  
M3062AFCTGP@PQFP100 [CX3021]  
M3062AFCVFP@PQFP100 [CX3022]  
M3062AFCVGP@PQFP100 [CX3021]  
M3062CF8TFP@PQFP100 [CX3022]  
M3062CF8TGP@PQFP100 [CX3021]  
M3062JFHTFP@PQFP100 [CX3022]



M3062JFHTFP@PQFP100(S) [CX3022] M3062JFHTGP@PQFP100 [CX3021]  
M3062JFHTGP@PQFP100(S) [CX3021] M3062JFHVFP@PQFP100 [CX3022]  
M3062JFHVFP@PQFP100(S) [CX3022] M3062JFHVGP@PQFP100 [CX3021]  
M3062JFHVGP@PQFP100(S) [CX3021] M3062LFGPFP@PQFP100 [CX3022]  
M3062LFGPFP@PQFP100(S) [CX3022] M3062LFGPGP@TQFP100 [CX3021]  
M3062LFGPGP@TQFP100(S) [CX3021] M306N4FCFP@PQFP100 [CX3022]  
M306N4FCGP@QFP100 [CX3021] M306N4FCTFP@PQFP100 [CX3022]  
M306N4FCTGP@QFP100 [CX3021] M306N4FCVFP@PQFP100 [CX3022]  
M306N4FCVGP@QFP100 [CX3021] M306N4FGFP@PQFP100 [CX3022]  
M306N4FGGP@QFP100 [CX3021] M306N4FGTFF@PQFP100 [CX3022]  
M306N4FGTGP@QFP100 [CX3021] M306N4FGVFP@PQFP100 [CX3022]  
M306N4FGVGP@QFP100 [CX3021] M306N5FCFP@PQFP100 [CX3022]  
M306N5FCGP@QFP100 [CX3021] M306N5FCTFP@PQFP100 [CX3022]  
M306N5FCTGP@QFP100 [CX3021] M306N5FCVFP@PQFP100 [CX3022]  
M306N5FCVGP@QFP100 [CX3021] M306NAFGTFF@PQFP100 [CX3022]  
M306NBFCTFP@PQFP100 [CX3022] M306NKFHGP@QFP100 [CX3021]  
M306NKFHTGP@QFP100 [CX3021] M306NKFHVGP@QFP100 [CX3021]  
M306NKFJGP@QFP100 [CX3021] M306NKFJTGP@QFP100 [CX3021]  
M306NKFJVGP@QFP100 [CX3021] M306NLFHGP@QFP100 [CX3021]  
M306NLFHTGP@QFP100 [CX3021] M306NLFHVGP@QFP100 [CX3021]  
M306NLFJGP@QFP100 [CX3021] M306NLFJTG@QFP100 [CX3021]  
M306NLFJVGP@QFP100 [CX3021] M30833FJFP@PQFP100 [CX3022]  
M30833FJGP@TQFP100 [CX3021] M30833FJTGP@TQFP100 [CX3021]  
M30873FHGP@TQFP100 [CX3021] M30876FJGP@TQFP100 [CX3021]  
M30879FKGP@TQFP100 [CX3021] M30879FLFP@TQFP100 [CX3022]  
M30879FLGP@TQFP100 [CX3021] M34283G2GP [CX1067]  
M34286G2GP [CX1067] M34508G4FP [CX1031]  
M34508G4GP [CX1067] M34508G4HFP [CX1031]  
M34508G4HGP [CX1067] M34509G4FP [CX1047]  
M34509G4HFP [CX1047] M34559G6FP@QFP52 [CX3010]  
M3455AG8FP@QFP52 [CX3010] M3455AGCFP@QFP52 [CX3010]  
M37531E4FP@SSOP36 [CX1056] M37531E8FP@SSOP36 [CX1056]  
M37544G2(GP)@LQFP32 [CX3001] M37544G2(SP)@SDIP32 [CX0032]  
M37544G2A(GP)@LQFP32 [CX3001] M37544G2A(SP)@SDIP32 [CX0032]  
M37545G4(FP)@SSOP36 [CX1046] M37545G4(GP)@LQFP32 [CX3001]  
M37545G6(FP)@SSOP36 [CX1046] M37545G6(GP)@LQFP32 [CX3001]  
M37545G8(FP)@SSOP36 [CX1046] M37545G8(GP)@LQFP32 [CX3001]  
M37546G2(FP)@SSOP36 [CX1046] M37546G2(GP)@LQFP32 [CX3001]  
M37546G2(SP)@SDIP32 [CX0032] M37546G4(FP)@SSOP36 [CX1046]  
M37546G4(GP)@LQFP32 [CX3001] M37546G4(SP)@SDIP32 [CX0032]  
M37547G2(FP)@SSOP36 [CX1046] M37547G4(FP)@SSOP36 [CX1046]  
M37548G1(FP)@TSSOP20 [CX1000] M37548G2(FP)@TSSOP20 [CX1000]  
M37548G3(FP)@TSSOP20 [CX1000] M37549G1FP@SSOP24 [CX1047]  
M37549G1SP@SDIP24 [CX0032] M37549G2FP@SSOP24 [CX1047]  
M37549G2SP@SDIP24 [CX0032] M37549G3FP@SSOP24 [CX1047]  
M37549G3SP@SDIP24 [CX0032] M38039FFHFP@QFP64 [CX3044]  
M38039FFHHP@QFP64 [CX3011] M38039FFHGP@QFP64 [CX3044]  
M38039FFHSP@SDIP64 [CX0064] M38234G4(FP)@PQFP80 [CX3020]  
M38234G4(HP)@TQFP80 [CX3016] M38235G6(FP)@PQFP80 [CX3020]  
M38235G6(HP)@TQFP80 [CX3016] M38238G8(FP)@PQFP80 [CX3020]  
M38238G8(HP)@TQFP80 [CX3016] M38239GC(FP)@PQFP80 [CX3020]  
M38239GC(HP)@TQFP80 [CX3016] M3823AGF(FP)@PQFP80 [CX3020]  
M3823AGF(HP)@TQFP80 [CX3016] M38503G4A(FP)@SSOP42 [CX1046]  
M38503G4A(SP)@SDIP42 [CX0042] M38507F8FP@SSOP42 [CX1056]  
M38507F8SP@SDIP42 [CX0042] M38588G6(FP)@SSOP42 [CX1046]  
M38588G6(SP)@SDIP42 [CX0042] M38588G8(FP)@SSOP42 [CX1046]  
M38588G8(SP)@SDIP42 [CX0042] M38588GC(FP)@SSOP42 [CX1046]  
M38588GC(SP)@SDIP42 [CX0042] M38859FFHP@QFP80 [CX3016]  
M38D24G4(FP)@QFP64 [CX3013] M38D24G4(HP)@QFP64 [CX3011]

M38D24G6(FP)@QFP64 [CX3013] M38D24G6(HP)@QFP64 [CX3011]  
M38D28G8(FP)@QFP64 [CX3013] M38D28G8(HP)@QFP64 [CX3011]  
M38D29FF(HP)@QFP64 [CX3011] M38D29GC(FP)@QFP64 [CX3013]  
M38D29GC(HP)@QFP64 [CX3011] M38D29GF(FP)@QFP64 [CX3013]  
M38D29GF(HP)@QFP64 [CX3011] M38D58G8FP@PQFP80 [CX3020]  
M38D58G8HP@QFP80 [CX3016] M38D59FFFF@PQFP80 [CX3020]  
M38D59FFHP@QFP80 [CX3016] M38D59GCF@PQFP80 [CX3020]  
M38D59GCHP@QFP80 [CX3016] M38D59GFF@PQFP80 [CX3020]  
M38D59GFHP@QFP80 [CX3016] M3NN00FETGP@QFP100 [CX3021]  
M3NN00FETGP@QFP100(S) [CX3021] R5F21102DFP@TQFP32 [CX3001]  
R5F21102FP@TQFP32 [CX3001] R5F21103DFP@TQFP32 [CX3001]  
R5F21103FP@TQFP32 [CX3001] R5F21104DFP@TQFP32 [CX3001]  
R5F21104FP@TQFP32 [CX3001] R5F21112DFP@TQFP32 [CX3001]  
R5F21112FP@TQFP32 [CX3001] R5F21113DFP@TQFP32 [CX3001]  
R5F21113FP@TQFP32 [CX3001] R5F21114DFP@TQFP32 [CX3001]  
R5F21114FP@TQFP32 [CX3001] R5F21122DFP@TQFP32 [CX3001]  
R5F21122FP@TQFP32 [CX3001] R5F21123DFP@TQFP32 [CX3001]  
R5F21123FP@TQFP32 [CX3001] R5F21124DFP@TQFP32 [CX3001]  
R5F21124FP@TQFP32 [CX3001] R5F21132DFP@TQFP32 [CX3001]  
R5F21132FP@TQFP32 [CX3001] R5F21133DFP@TQFP32 [CX3001]  
R5F21133FP@TQFP32 [CX3001] R5F21134DFP@TQFP32 [CX3001]  
R5F21134FP@TQFP32 [CX3001] R5F21142DSP@TSSOP20 [CX1000]  
R5F21142DSP@TSSOP20(single ISP) [CX0001]  
R5F21142DSP@TSSOP20(single wire) [CX1000]  
R5F21142DSP@TSSOP20(UART ISP) [CX0001]  
R5F21142DSP@TSSOP20(UART mode) [CX1000]  
R5F21142SP@TSSOP20 [CX1000]  
R5F21142SP@TSSOP20(single ISP) [CX0001]  
R5F21142SP@TSSOP20(single wire) [CX1000]  
R5F21142SP@TSSOP20(UART ISP) [CX0001]  
R5F21142SP@TSSOP20(UART mode) [CX1000]  
R5F21143DSP@TSSOP20 [CX1000]  
R5F21143DSP@TSSOP20(single ISP) [CX0001]  
R5F21143DSP@TSSOP20(single wire) [CX1000]  
R5F21143DSP@TSSOP20(UART ISP) [CX0001]  
R5F21143DSP@TSSOP20(UART mode) [CX1000]  
R5F21143SP@TSSOP20 [CX1000]  
R5F21143SP@TSSOP20(single ISP) [CX0001]  
R5F21143SP@TSSOP20(single wire) [CX1000]  
R5F21143SP@TSSOP20(UART ISP) [CX0001]  
R5F21143SP@TSSOP20(UART mode) [CX1000]  
R5F21144DSP@TSSOP20 [CX1000]  
R5F21144DSP@TSSOP20(single ISP) [CX0001]  
R5F21144DSP@TSSOP20(single wire) [CX1000]  
R5F21144DSP@TSSOP20(UART ISP) [CX0001]  
R5F21144DSP@TSSOP20(UART mode) [CX1000]  
R5F21144SP@TSSOP20 [CX1000]  
R5F21144SP@TSSOP20(single ISP) [CX0001]  
R5F21144SP@TSSOP20(single wire) [CX1000]  
R5F21144SP@TSSOP20(UART ISP) [CX0001]  
R5F21144SP@TSSOP20(UART mode) [CX1000]  
R5F21152DSP@TSSOP20 [CX1000]  
R5F21152DSP@TSSOP20(single ISP) [CX0001]  
R5F21152DSP@TSSOP20(single wire) [CX1000]  
R5F21152DSP@TSSOP20(UART ISP) [CX0001]  
R5F21152DSP@TSSOP20(UART mode) [CX1000]  
R5F21152SP@TSSOP20 [CX1000]  
R5F21152SP@TSSOP20(single ISP) [CX0001]  
R5F21152SP@TSSOP20(single wire) [CX1000]

R5F21152SP@TSSOP20(UART ISP) [CX0001]  
R5F21152SP@TSSOP20(UART mode) [CX1000]  
R5F21153DSP@TSSOP20 [CX1000]  
R5F21153DSP@TSSOP20(single ISP) [CX0001]  
R5F21153DSP@TSSOP20(single wire) [CX1000]  
R5F21153DSP@TSSOP20(UART ISP) [CX0001]  
R5F21153DSP@TSSOP20(UART mode) [CX1000]  
R5F21153SP@TSSOP20 [CX1000]  
R5F21153SP@TSSOP20(single ISP) [CX0001]  
R5F21153SP@TSSOP20(single wire) [CX1000]  
R5F21153SP@TSSOP20(UART ISP) [CX0001]  
R5F21153SP@TSSOP20(UART mode) [CX1000]  
R5F21154DSP@TSSOP20 [CX1000]  
R5F21154DSP@TSSOP20(single ISP) [CX0001]  
R5F21154DSP@TSSOP20(single wire) [CX1000]  
R5F21154DSP@TSSOP20(UART ISP) [CX0001]  
R5F21154DSP@TSSOP20(UART mode) [CX1000]  
R5F21154SP@TSSOP20 [CX1000]  
R5F21154SP@TSSOP20(single ISP) [CX0001]  
R5F21154SP@TSSOP20(single wire) [CX1000]  
R5F21154SP@TSSOP20(UART ISP) [CX0001]  
R5F21154SP@TSSOP20(UART mode) [CX1000]  
R5F21162DSP@TSSOP20 [CX1000]  
R5F21162DSP@TSSOP20(single ISP) [CX0001]  
R5F21162DSP@TSSOP20(single wire) [CX1000]  
R5F21162DSP@TSSOP20(UART ISP) [CX0001]  
R5F21162DSP@TSSOP20(UART mode) [CX1000]  
R5F21162SP@TSSOP20 [CX1000]  
R5F21162SP@TSSOP20(single ISP) [CX0001]  
R5F21162SP@TSSOP20(single wire) [CX1000]  
R5F21162SP@TSSOP20(UART ISP) [CX0001]  
R5F21162SP@TSSOP20(UART mode) [CX1000]  
R5F21163DSP@TSSOP20 [CX1000]  
R5F21163DSP@TSSOP20(single ISP) [CX0001]  
R5F21163DSP@TSSOP20(single wire) [CX1000]  
R5F21163DSP@TSSOP20(UART ISP) [CX0001]  
R5F21163DSP@TSSOP20(UART mode) [CX1000]  
R5F21163SP@TSSOP20 [CX1000]  
R5F21163SP@TSSOP20(single ISP) [CX0001]  
R5F21163SP@TSSOP20(single wire) [CX1000]  
R5F21163SP@TSSOP20(UART ISP) [CX0001]  
R5F21163SP@TSSOP20(UART mode) [CX1000]  
R5F21164DSP@TSSOP20 [CX1000]  
R5F21164DSP@TSSOP20(single ISP) [CX0001]  
R5F21164DSP@TSSOP20(single wire) [CX1000]  
R5F21164DSP@TSSOP20(UART ISP) [CX0001]  
R5F21164DSP@TSSOP20(UART mode) [CX1000]  
R5F21164SP@TSSOP20 [CX1000]  
R5F21164SP@TSSOP20(single ISP) [CX0001]  
R5F21164SP@TSSOP20(single wire) [CX1000]  
R5F21164SP@TSSOP20(UART ISP) [CX0001]  
R5F21164SP@TSSOP20(UART mode) [CX1000]  
R5F21172DSP@TSSOP20 [CX1000]  
R5F21172DSP@TSSOP20(single ISP) [CX0001]  
R5F21172DSP@TSSOP20(single wire) [CX1000]  
R5F21172DSP@TSSOP20(UART ISP) [CX0001]  
R5F21172DSP@TSSOP20(UART mode) [CX1000]  
R5F21172SP@TSSOP20 [CX1000]  
R5F21172SP@TSSOP20(single ISP) [CX0001]

R5F21172SP@TSSOP20(single wire) [CX1000]  
R5F21172SP@TSSOP20(UART ISP) [CX0001]  
R5F21172SP@TSSOP20(UART mode) [CX1000]  
R5F21173DSP@TSSOP20 [CX1000]  
R5F21173DSP@TSSOP20(single ISP) [CX0001]  
R5F21173DSP@TSSOP20(single wire) [CX1000]  
R5F21173DSP@TSSOP20(UART ISP) [CX0001]  
R5F21173DSP@TSSOP20(UART mode) [CX1000]  
R5F21173SP@TSSOP20 [CX1000]  
R5F21173SP@TSSOP20(single ISP) [CX0001]  
R5F21173SP@TSSOP20(single wire) [CX1000]  
R5F21173SP@TSSOP20(UART ISP) [CX0001]  
R5F21173SP@TSSOP20(UART mode) [CX1000]  
R5F21174DSP@TSSOP20 [CX1000]  
R5F21174DSP@TSSOP20(single ISP) [CX0001]  
R5F21174DSP@TSSOP20(single wire) [CX1000]  
R5F21174DSP@TSSOP20(UART ISP) [CX0001]  
R5F21174DSP@TSSOP20(UART mode) [CX1000]  
R5F21174SP@TSSOP20 [CX1000]  
R5F21174SP@TSSOP20(single ISP) [CX0001]  
R5F21174SP@TSSOP20(single wire) [CX1000]  
R5F21174SP@TSSOP20(UART ISP) [CX0001]  
R5F21174SP@TSSOP20(UART mode) [CX1000]  
R5F21181DD@SDIP20 [CX0032]  
R5F21181DD@SDIP20(single ISP) [CX0001]  
R5F21181DD@SDIP20(single wire) [CX0032]  
R5F21181DD@SDIP20(UART ISP) [CX0001]  
R5F21181DD@SDIP20(UART mode) [CX0032]  
R5F21181DSP@TSSOP20 [CX1000]  
R5F21181DSP@TSSOP20(single ISP) [CX0001]  
R5F21181DSP@TSSOP20(single wire) [CX1000]  
R5F21181DSP@TSSOP20(UART ISP) [CX0001]  
R5F21181DSP@TSSOP20(UART mode) [CX1000]  
R5F21181SP@TSSOP20 [CX1000]  
R5F21181SP@TSSOP20(single ISP) [CX0001]  
R5F21181SP@TSSOP20(single wire) [CX1000]  
R5F21181SP@TSSOP20(UART ISP) [CX0001]  
R5F21181SP@TSSOP20(UART mode) [CX1000]  
R5F21182DD@SDIP20 [CX0032]  
R5F21182DD@SDIP20(single ISP) [CX0001]  
R5F21182DD@SDIP20(single wire) [CX0032]  
R5F21182DD@SDIP20(UART ISP) [CX0001]  
R5F21182DD@SDIP20(UART mode) [CX0032]  
R5F21182DSP@TSSOP20 [CX1000]  
R5F21182DSP@TSSOP20(single ISP) [CX0001]  
R5F21182DSP@TSSOP20(single wire) [CX1000]  
R5F21182DSP@TSSOP20(UART ISP) [CX0001]  
R5F21182DSP@TSSOP20(UART mode) [CX1000]  
R5F21182NP@QFN28 [CX4013]  
R5F21182NP@QFN28(single ISP) [CX0001]  
R5F21182NP@QFN28(single wire) [CX4013]  
R5F21182NP@QFN28(UART ISP) [CX0001]  
R5F21182NP@QFN28(UART mode) [CX4013]  
R5F21182SP@TSSOP20 [CX1000]  
R5F21182SP@TSSOP20(single ISP) [CX0001]  
R5F21182SP@TSSOP20(single wire) [CX1000]  
R5F21182SP@TSSOP20(UART ISP) [CX0001]  
R5F21182SP@TSSOP20(UART mode) [CX1000]  
R5F21183DD@SDIP20 [CX0032]

R5F21183DD@SDIP20(single ISP) [CX0001]  
R5F21183DD@SDIP20(single wire) [CX0032]  
R5F21183DD@SDIP20(UART ISP) [CX0001]  
R5F21183DD@SDIP20(UART mode) [CX0032]  
R5F21183DSP@TSSOP20 [CX1000]  
R5F21183DSP@TSSOP20(single ISP) [CX0001]  
R5F21183DSP@TSSOP20(single wire) [CX1000]  
R5F21183DSP@TSSOP20(UART ISP) [CX0001]  
R5F21183DSP@TSSOP20(UART mode) [CX1000]  
R5F21183NP@QFN28 [CX4013]  
R5F21183NP@QFN28(single ISP) [CX0001]  
R5F21183NP@QFN28(single wire) [CX4013]  
R5F21183NP@QFN28(UART ISP) [CX0001]  
R5F21183NP@QFN28(UART mode) [CX4013]  
R5F21183SP@TSSOP20 [CX1000]  
R5F21183SP@TSSOP20(single ISP) [CX0001]  
R5F21183SP@TSSOP20(single wire) [CX1000]  
R5F21183SP@TSSOP20(UART ISP) [CX0001]  
R5F21183SP@TSSOP20(UART mode) [CX1000]  
R5F21184DD@SDIP20 [CX0032]  
R5F21184DD@SDIP20(single ISP) [CX0001]  
R5F21184DD@SDIP20(single wire) [CX0032]  
R5F21184DD@SDIP20(UART ISP) [CX0001]  
R5F21184DD@SDIP20(UART mode) [CX0032]  
R5F21184DSP@TSSOP20 [CX1000]  
R5F21184DSP@TSSOP20(single ISP) [CX0001]  
R5F21184DSP@TSSOP20(single wire) [CX1000]  
R5F21184DSP@TSSOP20(UART ISP) [CX0001]  
R5F21184DSP@TSSOP20(UART mode) [CX1000]  
R5F21184NP@QFN28 [CX4013]  
R5F21184NP@QFN28(single ISP) [CX0001]  
R5F21184NP@QFN28(single wire) [CX4013]  
R5F21184NP@QFN28(UART ISP) [CX0001]  
R5F21184NP@QFN28(UART mode) [CX4013]  
R5F21184SP@TSSOP20 [CX1000]  
R5F21184SP@TSSOP20(single ISP) [CX0001]  
R5F21184SP@TSSOP20(single wire) [CX1000]  
R5F21184SP@TSSOP20(UART ISP) [CX0001]  
R5F21184SP@TSSOP20(UART mode) [CX1000]  
R5F21191DD@SDIP20 [CX0032]  
R5F21191DD@SDIP20(single ISP) [CX0001]  
R5F21191DD@SDIP20(single wire) [CX0032]  
R5F21191DD@SDIP20(UART ISP) [CX0001]  
R5F21191DD@SDIP20(UART mode) [CX0032]  
R5F21191DSP@TSSOP20 [CX1000]  
R5F21191DSP@TSSOP20(single ISP) [CX0001]  
R5F21191DSP@TSSOP20(single wire) [CX1000]  
R5F21191DSP@TSSOP20(UART ISP) [CX0001]  
R5F21191DSP@TSSOP20(UART mode) [CX1000]  
R5F21191SP@TSSOP20 [CX1000]  
R5F21191SP@TSSOP20(single ISP) [CX0001]  
R5F21191SP@TSSOP20(single wire) [CX1000]  
R5F21191SP@TSSOP20(UART ISP) [CX0001]  
R5F21191SP@TSSOP20(UART mode) [CX1000]  
R5F21192DD@SDIP20 [CX0032]  
R5F21192DD@SDIP20(single ISP) [CX0001]  
R5F21192DD@SDIP20(single wire) [CX0032]  
R5F21192DD@SDIP20(UART ISP) [CX0001]  
R5F21192DD@SDIP20(UART mode) [CX0032]

R5F21192DSP@TSSOP20 [CX1000]  
R5F21192DSP@TSSOP20(single ISP) [CX0001]  
R5F21192DSP@TSSOP20(single wire) [CX1000]  
R5F21192DSP@TSSOP20(UART ISP) [CX0001]  
R5F21192DSP@TSSOP20(UART mode) [CX1000]  
R5F21192NP@QFN28 [CX4013]  
R5F21192NP@QFN28(single ISP) [CX0001]  
R5F21192NP@QFN28(single wire) [CX4013]  
R5F21192NP@QFN28(UART ISP) [CX0001]  
R5F21192NP@QFN28(UART mode) [CX4013]  
R5F21192SP@TSSOP20 [CX1000]  
R5F21192SP@TSSOP20(single ISP) [CX0001]  
R5F21192SP@TSSOP20(single wire) [CX1000]  
R5F21192SP@TSSOP20(UART ISP) [CX0001]  
R5F21192SP@TSSOP20(UART mode) [CX1000]  
R5F21193DD@SDIP20 [CX0032]  
R5F21193DD@SDIP20(single ISP) [CX0001]  
R5F21193DD@SDIP20(single wire) [CX0032]  
R5F21193DD@SDIP20(UART ISP) [CX0001]  
R5F21193DD@SDIP20(UART mode) [CX0032]  
R5F21193DSP@TSSOP20 [CX1000]  
R5F21193DSP@TSSOP20(single ISP) [CX0001]  
R5F21193DSP@TSSOP20(single wire) [CX1000]  
R5F21193DSP@TSSOP20(UART ISP) [CX0001]  
R5F21193DSP@TSSOP20(UART mode) [CX1000]  
R5F21193NP@QFN28 [CX4013]  
R5F21193NP@QFN28(single ISP) [CX0001]  
R5F21193NP@QFN28(single wire) [CX4013]  
R5F21193NP@QFN28(UART ISP) [CX0001]  
R5F21193NP@QFN28(UART mode) [CX4013]  
R5F21193SP@TSSOP20 [CX1000]  
R5F21193SP@TSSOP20(single ISP) [CX0001]  
R5F21193SP@TSSOP20(single wire) [CX1000]  
R5F21193SP@TSSOP20(UART ISP) [CX0001]  
R5F21193SP@TSSOP20(UART mode) [CX1000]  
R5F21194DD@SDIP20 [CX0032]  
R5F21194DD@SDIP20(single ISP) [CX0001]  
R5F21194DD@SDIP20(single wire) [CX0032]  
R5F21194DD@SDIP20(UART ISP) [CX0001]  
R5F21194DD@SDIP20(UART mode) [CX0032]  
R5F21194DSP@TSSOP20 [CX1000]  
R5F21194DSP@TSSOP20(single ISP) [CX0001]  
R5F21194DSP@TSSOP20(single wire) [CX1000]  
R5F21194DSP@TSSOP20(UART ISP) [CX0001]  
R5F21194DSP@TSSOP20(UART mode) [CX1000]  
R5F21194NP@QFN28 [CX4013]  
R5F21194NP@QFN28(single ISP) [CX0001]  
R5F21194NP@QFN28(single wire) [CX4013]  
R5F21194NP@QFN28(UART ISP) [CX0001]  
R5F21194NP@QFN28(UART mode) [CX4013]  
R5F21194SP@TSSOP20 [CX1000]  
R5F21194SP@TSSOP20(single ISP) [CX0001]  
R5F21194SP@TSSOP20(single wire) [CX1000]  
R5F21194SP@TSSOP20(UART ISP) [CX0001]  
R5F21194SP@TSSOP20(UART mode) [CX1000]  
R5F211A1DD@SDIP20 [CX0032]  
R5F211A1DD@SDIP20(single ISP) [CX0001]  
R5F211A1DD@SDIP20(single wire) [CX0032]  
R5F211A1DD@SDIP20(UART ISP) [CX0001]

R5F211A1DD@SDIP20(UART mode) [CX0032]  
R5F211A1DSP@TSSOP20 [CX1000]  
R5F211A1DSP@TSSOP20(single ISP) [CX0001]  
R5F211A1DSP@TSSOP20(single wire) [CX1000]  
R5F211A1DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A1DSP@TSSOP20(UART mode) [CX1000]  
R5F211A1SP@TSSOP20 [CX1000]  
R5F211A1SP@TSSOP20(single ISP) [CX0001]  
R5F211A1SP@TSSOP20(single wire) [CX1000]  
R5F211A1SP@TSSOP20(UART ISP) [CX0001]  
R5F211A1SP@TSSOP20(UART mode) [CX1000]  
R5F211A2DD@SDIP20 [CX0032]  
R5F211A2DD@SDIP20(single ISP) [CX0001]  
R5F211A2DD@SDIP20(single wire) [CX0032]  
R5F211A2DD@SDIP20(UART ISP) [CX0001]  
R5F211A2DD@SDIP20(UART mode) [CX0032]  
R5F211A2DSP@TSSOP20 [CX1000]  
R5F211A2DSP@TSSOP20(single ISP) [CX0001]  
R5F211A2DSP@TSSOP20(single wire) [CX1000]  
R5F211A2DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A2DSP@TSSOP20(UART mode) [CX1000]  
R5F211A2NP@QFN28 [CX4013]  
R5F211A2NP@QFN28(single ISP) [CX0001]  
R5F211A2NP@QFN28(single wire) [CX4013]  
R5F211A2NP@QFN28(UART ISP) [CX0001]  
R5F211A2NP@QFN28(UART mode) [CX4013]  
R5F211A2SP@TSSOP20 [CX1000]  
R5F211A2SP@TSSOP20(single ISP) [CX0001]  
R5F211A2SP@TSSOP20(single wire) [CX1000]  
R5F211A2SP@TSSOP20(UART ISP) [CX0001]  
R5F211A2SP@TSSOP20(UART mode) [CX1000]  
R5F211A3DD@SDIP20 [CX0032]  
R5F211A3DD@SDIP20(single ISP) [CX0001]  
R5F211A3DD@SDIP20(single wire) [CX0032]  
R5F211A3DD@SDIP20(UART ISP) [CX0001]  
R5F211A3DD@SDIP20(UART mode) [CX0032]  
R5F211A3DSP@TSSOP20 [CX1000]  
R5F211A3DSP@TSSOP20(single ISP) [CX0001]  
R5F211A3DSP@TSSOP20(single wire) [CX1000]  
R5F211A3DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A3DSP@TSSOP20(UART mode) [CX1000]  
R5F211A3NP@QFN28 [CX4013]  
R5F211A3NP@QFN28(single ISP) [CX0001]  
R5F211A3NP@QFN28(single wire) [CX4013]  
R5F211A3NP@QFN28(UART ISP) [CX0001]  
R5F211A3NP@QFN28(UART mode) [CX4013]  
R5F211A3SP@TSSOP20 [CX1000]  
R5F211A3SP@TSSOP20(single ISP) [CX0001]  
R5F211A3SP@TSSOP20(single wire) [CX1000]  
R5F211A3SP@TSSOP20(UART ISP) [CX0001]  
R5F211A3SP@TSSOP20(UART mode) [CX1000]  
R5F211A4DD@SDIP20 [CX0032]  
R5F211A4DD@SDIP20(single ISP) [CX0001]  
R5F211A4DD@SDIP20(single wire) [CX0032]  
R5F211A4DD@SDIP20(UART ISP) [CX0001]  
R5F211A4DD@SDIP20(UART mode) [CX0032]  
R5F211A4DSP@TSSOP20 [CX1000]  
R5F211A4DSP@TSSOP20(single ISP) [CX0001]  
R5F211A4DSP@TSSOP20(single wire) [CX1000]

R5F211A4DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A4DSP@TSSOP20(UART mode) [CX1000]  
R5F211A4NP@QFN28 [CX4013]  
R5F211A4NP@QFN28(single ISP) [CX0001]  
R5F211A4NP@QFN28(single wire) [CX4013]  
R5F211A4NP@QFN28(UART ISP) [CX0001]  
R5F211A4NP@QFN28(UART mode) [CX4013]  
R5F211A4SP@TSSOP20 [CX1000]  
R5F211A4SP@TSSOP20(single ISP) [CX0001]  
R5F211A4SP@TSSOP20(single wire) [CX1000]  
R5F211A4SP@TSSOP20(UART ISP) [CX0001]  
R5F211A4SP@TSSOP20(UART mode) [CX1000]  
R5F211B1DD@SDIP20 [CX0032]  
R5F211B1DD@SDIP20(single ISP) [CX0001]  
R5F211B1DD@SDIP20(single wire) [CX0032]  
R5F211B1DD@SDIP20(UART ISP) [CX0001]  
R5F211B1DD@SDIP20(UART mode) [CX0032]  
R5F211B1DSP@TSSOP20 [CX1000]  
R5F211B1DSP@TSSOP20(single ISP) [CX0001]  
R5F211B1DSP@TSSOP20(single wire) [CX1000]  
R5F211B1DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B1DSP@TSSOP20(UART mode) [CX1000]  
R5F211B1SP@TSSOP20 [CX1000]  
R5F211B1SP@TSSOP20(single ISP) [CX0001]  
R5F211B1SP@TSSOP20(single wire) [CX1000]  
R5F211B1SP@TSSOP20(UART ISP) [CX0001]  
R5F211B1SP@TSSOP20(UART mode) [CX1000]  
R5F211B2DD@SDIP20 [CX0032]  
R5F211B2DD@SDIP20(single ISP) [CX0001]  
R5F211B2DD@SDIP20(single wire) [CX0032]  
R5F211B2DD@SDIP20(UART ISP) [CX0001]  
R5F211B2DD@SDIP20(UART mode) [CX0032]  
R5F211B2DSP@TSSOP20 [CX1000]  
R5F211B2DSP@TSSOP20(single ISP) [CX0001]  
R5F211B2DSP@TSSOP20(single wire) [CX1000]  
R5F211B2DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B2DSP@TSSOP20(UART mode) [CX1000]  
R5F211B2NP@QFN28 [CX4013]  
R5F211B2NP@QFN28(single ISP) [CX0001]  
R5F211B2NP@QFN28(single wire) [CX4013]  
R5F211B2NP@QFN28(UART ISP) [CX0001]  
R5F211B2NP@QFN28(UART mode) [CX4013]  
R5F211B2SP@TSSOP20 [CX1000]  
R5F211B2SP@TSSOP20(single ISP) [CX0001]  
R5F211B2SP@TSSOP20(single wire) [CX1000]  
R5F211B2SP@TSSOP20(UART ISP) [CX0001]  
R5F211B2SP@TSSOP20(UART mode) [CX1000]  
R5F211B3DD@SDIP20 [CX0032]  
R5F211B3DD@SDIP20(single ISP) [CX0001]  
R5F211B3DD@SDIP20(single wire) [CX0032]  
R5F211B3DD@SDIP20(UART ISP) [CX0001]  
R5F211B3DD@SDIP20(UART mode) [CX0032]  
R5F211B3DSP@TSSOP20 [CX1000]  
R5F211B3DSP@TSSOP20(single ISP) [CX0001]  
R5F211B3DSP@TSSOP20(single wire) [CX1000]  
R5F211B3DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B3DSP@TSSOP20(UART mode) [CX1000]  
R5F211B3NP@QFN28 [CX4013]  
R5F211B3NP@QFN28(single ISP) [CX0001]



R5F211B3NP@QFN28(single wire) [CX4013]  
R5F211B3NP@QFN28(UART ISP) [CX0001]  
R5F211B3NP@QFN28(UART mode) [CX4013]  
R5F211B3SP@TSSOP20 [CX1000]  
R5F211B3SP@TSSOP20(single ISP) [CX0001]  
R5F211B3SP@TSSOP20(single wire) [CX1000]  
R5F211B3SP@TSSOP20(UART ISP) [CX0001]  
R5F211B3SP@TSSOP20(UART mode) [CX1000]  
R5F211B4DD@SDIP20 [CX0032]  
R5F211B4DD@SDIP20(single ISP) [CX0001]  
R5F211B4DD@SDIP20(single wire) [CX0032]  
R5F211B4DD@SDIP20(UART ISP) [CX0001]  
R5F211B4DD@SDIP20(UART mode) [CX0032]  
R5F211B4DSP@TSSOP20 [CX1000]  
R5F211B4DSP@TSSOP20(single ISP) [CX0001]  
R5F211B4DSP@TSSOP20(single wire) [CX1000]  
R5F211B4DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B4DSP@TSSOP20(UART mode) [CX1000]  
R5F211B4NP@QFN28 [CX4013]  
R5F211B4NP@QFN28(single ISP) [CX0001]  
R5F211B4NP@QFN28(single wire) [CX4013]  
R5F211B4NP@QFN28(UART ISP) [CX0001]  
R5F211B4NP@QFN28(UART mode) [CX4013]  
R5F211B4SP@TSSOP20 [CX1000]  
R5F211B4SP@TSSOP20(single ISP) [CX0001]  
R5F211B4SP@TSSOP20(single wire) [CX1000]  
R5F211B4SP@TSSOP20(UART ISP) [CX0001]  
R5F211B4SP@TSSOP20(UART mode) [CX1000]  
R5F21206JFP@TQFP48 [CX3007]  
R5F21206JFP@TQFP48(single ISP) [CX0001]  
R5F21206JFP@TQFP48(single wire) [CX3007]  
R5F21206KFP@TQFP48 [CX3007]  
R5F21206KFP@TQFP48(single ISP) [CX0001]  
R5F21206KFP@TQFP48(single wire) [CX3007]  
R5F21207JFP@TQFP48 [CX3007]  
R5F21207JFP@TQFP48(single ISP) [CX0001]  
R5F21207JFP@TQFP48(single wire) [CX3007]  
R5F21207KFP@TQFP48 [CX3007]  
R5F21207KFP@TQFP48(single ISP) [CX0001]  
R5F21207KFP@TQFP48(single wire) [CX3007]  
R5F21208JFP@TQFP48 [CX3007]  
R5F21208JFP@TQFP48(single ISP) [CX0001]  
R5F21208JFP@TQFP48(single wire) [CX3007]  
R5F21208KFP@TQFP48 [CX3007]  
R5F21208KFP@TQFP48(single ISP) [CX0001]  
R5F21208KFP@TQFP48(single wire) [CX3007]  
R5F2120AJFP@TQFP48 [CX3007]  
R5F2120AJFP@TQFP48(single ISP) [CX0001]  
R5F2120AJFP@TQFP48(single wire) [CX3007]  
R5F2120AKFP@TQFP48 [CX3007]  
R5F2120AKFP@TQFP48(single ISP) [CX0001]  
R5F2120AKFP@TQFP48(single wire) [CX3007]  
R5F2120CJFP@TQFP48 [CX3007]  
R5F2120CJFP@TQFP48(single ISP) [CX0001]  
R5F2120CJFP@TQFP48(single wire) [CX3007]  
R5F2120CKFP@TQFP48 [CX3007]  
R5F2120CKFP@TQFP48(single ISP) [CX0001]  
R5F2120CKFP@TQFP48(single wire) [CX3007]  
R5F21216JFP@TQFP48 [CX3007]

R5F21216JFP@TQFP48(single ISP) [CX0001]  
R5F21216JFP@TQFP48(single wire) [CX3007]  
R5F21216KFP@TQFP48 [CX3007]  
R5F21216KFP@TQFP48(single ISP) [CX0001]  
R5F21216KFP@TQFP48(single wire) [CX3007]  
R5F21217JFP@TQFP48 [CX3007]  
R5F21217JFP@TQFP48(single ISP) [CX0001]  
R5F21217JFP@TQFP48(single wire) [CX3007]  
R5F21217KFP@TQFP48 [CX3007]  
R5F21217KFP@TQFP48(single ISP) [CX0001]  
R5F21217KFP@TQFP48(single wire) [CX3007]  
R5F21218JFP@TQFP48 [CX3007]  
R5F21218JFP@TQFP48(single ISP) [CX0001]  
R5F21218JFP@TQFP48(single wire) [CX3007]  
R5F21218KFP@TQFP48 [CX3007]  
R5F21218KFP@TQFP48(single ISP) [CX0001]  
R5F21218KFP@TQFP48(single wire) [CX3007]  
R5F2121AJFP@TQFP48 [CX3007]  
R5F2121AJFP@TQFP48(single ISP) [CX0001]  
R5F2121AJFP@TQFP48(single wire) [CX3007]  
R5F2121AKFP@TQFP48 [CX3007]  
R5F2121AKFP@TQFP48(single ISP) [CX0001]  
R5F2121AKFP@TQFP48(single wire) [CX3007]  
R5F2121CJFP@TQFP48 [CX3007]  
R5F2121CJFP@TQFP48(single ISP) [CX0001]  
R5F2121CJFP@TQFP48(single wire) [CX3007]  
R5F2121CKFP@TQFP48 [CX3007]  
R5F2121CKFP@TQFP48(single ISP) [CX0001]  
R5F2121CKFP@TQFP48(single wire) [CX3007]  
R5F21226JFP@TQFP48 [CX3007]  
R5F21226JFP@TQFP48(single ISP) [CX0001]  
R5F21226JFP@TQFP48(single wire) [CX3007]  
R5F21226KFP@TQFP48 [CX3007]  
R5F21226KFP@TQFP48(single ISP) [CX0001]  
R5F21226KFP@TQFP48(single wire) [CX3007]  
R5F21227JFP@TQFP48 [CX3007]  
R5F21227JFP@TQFP48(single ISP) [CX0001]  
R5F21227JFP@TQFP48(single wire) [CX3007]  
R5F21227KFP@TQFP48 [CX3007]  
R5F21227KFP@TQFP48(single ISP) [CX0001]  
R5F21227KFP@TQFP48(single wire) [CX3007]  
R5F21228JFP@TQFP48 [CX3007]  
R5F21228JFP@TQFP48(single ISP) [CX0001]  
R5F21228JFP@TQFP48(single wire) [CX3007]  
R5F21228KFP@TQFP48 [CX3007]  
R5F21228KFP@TQFP48(single ISP) [CX0001]  
R5F21228KFP@TQFP48(single wire) [CX3007]  
R5F2122AJFP@TQFP48 [CX3007]  
R5F2122AJFP@TQFP48(single ISP) [CX0001]  
R5F2122AJFP@TQFP48(single wire) [CX3007]  
R5F2122AKFP@TQFP48 [CX3007]  
R5F2122AKFP@TQFP48(single ISP) [CX0001]  
R5F2122AKFP@TQFP48(single wire) [CX3007]  
R5F2122CJFP@TQFP48 [CX3007]  
R5F2122CJFP@TQFP48(single ISP) [CX0001]  
R5F2122CJFP@TQFP48(single wire) [CX3007]  
R5F2122CKFP@TQFP48 [CX3007]  
R5F2122CKFP@TQFP48(single ISP) [CX0001]  
R5F2122CKFP@TQFP48(single wire) [CX3007]

R5F21236DFP@TQFP48 [CX3007]  
R5F21236DFP@TQFP48(single wire) [CX3007]  
R5F21236JFP@TQFP48 [CX3007]  
R5F21236JFP@TQFP48(single ISP) [CX0001]  
R5F21236JFP@TQFP48(single wire) [CX3007]  
R5F21236KFP@TQFP48 [CX3007]  
R5F21236KFP@TQFP48(single ISP) [CX0001]  
R5F21236KFP@TQFP48(single wire) [CX3007]  
R5F21237JFP@TQFP48 [CX3007]  
R5F21237JFP@TQFP48(single ISP) [CX0001]  
R5F21237JFP@TQFP48(single wire) [CX3007]  
R5F21237KFP@TQFP48 [CX3007]  
R5F21237KFP@TQFP48(single ISP) [CX0001]  
R5F21237KFP@TQFP48(single wire) [CX3007]  
R5F21238JFP@TQFP48 [CX3007]  
R5F21238JFP@TQFP48(single ISP) [CX0001]  
R5F21238JFP@TQFP48(single wire) [CX3007]  
R5F21238KFP@TQFP48 [CX3007]  
R5F21238KFP@TQFP48(single ISP) [CX0001]  
R5F21238KFP@TQFP48(single wire) [CX3007]  
R5F2123AJFP@TQFP48 [CX3007]  
R5F2123AJFP@TQFP48(single ISP) [CX0001]  
R5F2123AJFP@TQFP48(single wire) [CX3007]  
R5F2123AKFP@TQFP48 [CX3007]  
R5F2123AKFP@TQFP48(single ISP) [CX0001]  
R5F2123AKFP@TQFP48(single wire) [CX3007]  
R5F2123CJFP@TQFP48 [CX3007]  
R5F2123CJFP@TQFP48(single ISP) [CX0001]  
R5F2123CJFP@TQFP48(single wire) [CX3007]  
R5F2123CKFP@TQFP48 [CX3007]  
R5F2123CKFP@TQFP48(single ISP) [CX0001]  
R5F2123CKFP@TQFP48(single wire) [CX3007]  
R5F21244SDFP@TQFP52 [CX3010]  
R5F21244SDFP@TQFP52(single ISP) [CX0001]  
R5F21244SDFP@TQFP52(single wire) [CX3010]  
R5F21244SDFP@TQFP52(UART ISP) [CX0001]  
R5F21244SDFP@TQFP52(UART mode) [CX3010]  
R5F21244SNFP@TQFP52 [CX3010]  
R5F21244SNFP@TQFP52(single ISP) [CX0001]  
R5F21244SNFP@TQFP52(single wire) [CX3010]  
R5F21244SNFP@TQFP52(UART ISP) [CX0001]  
R5F21244SNFP@TQFP52(UART mode) [CX3010]  
R5F21245SDFP@TQFP52 [CX3010]  
R5F21245SDFP@TQFP52(single wire) [CX3010]  
R5F21245SDFP@TQFP52(UART ISP) [CX0001]  
R5F21245SDFP@TQFP52(UART mode) [CX3010]  
R5F21245SNFP@TQFP52 [CX3010]  
R5F21245SNFP@TQFP52(single wire) [CX3010]  
R5F21245SNFP@TQFP52(UART ISP) [CX0001]  
R5F21245SNFP@TQFP52(UART mode) [CX3010]  
R5F21246SDFP@TQFP52 [CX3010]  
R5F21246SDFP@TQFP52(single ISP) [CX0001]  
R5F21246SDFP@TQFP52(single wire) [CX3010]  
R5F21246SDFP@TQFP52(UART ISP) [CX0001]  
R5F21246SDFP@TQFP52(UART mode) [CX3010]  
R5F21246SNFP@TQFP52 [CX3010]  
R5F21246SNFP@TQFP52(single ISP) [CX0001]  
R5F21246SNFP@TQFP52(single wire) [CX3010]  
R5F21246SNFP@TQFP52(UART ISP) [CX0001]

R5F21246SNFP@TQFP52(UART mode) [CX3010]  
R5F21247SDFP@TQFP52 [CX3010]  
R5F21247SDFP@TQFP52(single ISP) [CX0001]  
R5F21247SDFP@TQFP52(single wire) [CX3010]  
R5F21247SDFP@TQFP52(UART ISP) [CX0001]  
R5F21247SDFP@TQFP52(UART mode) [CX3010]  
R5F21247SNFP@TQFP52 [CX3010]  
R5F21247SNFP@TQFP52(single ISP) [CX0001]  
R5F21247SNFP@TQFP52(single wire) [CX3010]  
R5F21247SNFP@TQFP52(UART ISP) [CX0001]  
R5F21247SNFP@TQFP52(UART mode) [CX3010]  
R5F21248SDFP@TQFP52 [CX3010]  
R5F21248SDFP@TQFP52(single ISP) [CX0001]  
R5F21248SDFP@TQFP52(single wire) [CX3010]  
R5F21248SDFP@TQFP52(UART ISP) [CX0001]  
R5F21248SDFP@TQFP52(UART mode) [CX3010]  
R5F21248SNFP@TQFP52 [CX3010]  
R5F21248SNFP@TQFP52(single ISP) [CX0001]  
R5F21248SNFP@TQFP52(single wire) [CX3010]  
R5F21248SNFP@TQFP52(UART ISP) [CX0001]  
R5F21248SNFP@TQFP52(UART mode) [CX3010]  
R5F21254SDFP@TQFP52 [CX3010]  
R5F21254SDFP@TQFP52(single ISP) [CX0001]  
R5F21254SDFP@TQFP52(single wire) [CX3010]  
R5F21254SDFP@TQFP52(UART ISP) [CX0001]  
R5F21254SDFP@TQFP52(UART mode) [CX3010]  
R5F21254SNFP@TQFP52 [CX3010]  
R5F21254SNFP@TQFP52(single ISP) [CX0001]  
R5F21254SNFP@TQFP52(single wire) [CX3010]  
R5F21254SNFP@TQFP52(UART ISP) [CX0001]  
R5F21254SNFP@TQFP52(UART mode) [CX3010]  
R5F21255SDFP@TQFP52 [CX3010]  
R5F21255SDFP@TQFP52(single wire) [CX3010]  
R5F21255SDFP@TQFP52(UART mode) [CX3010]  
R5F21255SNFP@TQFP52 [CX3010]  
R5F21255SNFP@TQFP52(single wire) [CX3010]  
R5F21255SNFP@TQFP52(UART mode) [CX3010]  
R5F21256SDFP@TQFP52 [CX3010]  
R5F21256SDFP@TQFP52(single ISP) [CX0001]  
R5F21256SDFP@TQFP52(single wire) [CX3010]  
R5F21256SDFP@TQFP52(UART ISP) [CX0001]  
R5F21256SDFP@TQFP52(UART mode) [CX3010]  
R5F21256SNFP@TQFP52 [CX3010]  
R5F21256SNFP@TQFP52(single ISP) [CX0001]  
R5F21256SNFP@TQFP52(single wire) [CX3010]  
R5F21256SNFP@TQFP52(UART ISP) [CX0001]  
R5F21256SNFP@TQFP52(UART mode) [CX3010]  
R5F21257SDFP@TQFP52 [CX3010]  
R5F21257SDFP@TQFP52(single ISP) [CX0001]  
R5F21257SDFP@TQFP52(single wire) [CX3010]  
R5F21257SDFP@TQFP52(UART ISP) [CX0001]  
R5F21257SDFP@TQFP52(UART mode) [CX3010]  
R5F21257SNFP@TQFP52 [CX3010]  
R5F21257SNFP@TQFP52(single ISP) [CX0001]  
R5F21257SNFP@TQFP52(single wire) [CX3010]  
R5F21257SNFP@TQFP52(UART ISP) [CX0001]  
R5F21257SNFP@TQFP52(UART mode) [CX3010]  
R5F21258SDFP@TQFP52 [CX3010]  
R5F21258SDFP@TQFP52(single ISP) [CX0001]

R5F21258SDFP@TQFP52(single wire) [CX3010]  
R5F21258SDFP@TQFP52(UART ISP) [CX0001]  
R5F21258SDFP@TQFP52(UART mode) [CX3010]  
R5F21258SNFP@TQFP52 [CX3010]  
R5F21258SNFP@TQFP52(single ISP) [CX0001]  
R5F21258SNFP@TQFP52(single wire) [CX3010]  
R5F21258SNFP@TQFP52(UART ISP) [CX0001]  
R5F21258SNFP@TQFP52(UART mode) [CX3010]  
R5F21262DFP@QFP32 [CX3061]  
R5F21262DFP@QFP32(single ISP) [CX0001]  
R5F21262DFP@QFP32(single wire) [CX3061]  
R5F21262DFP@QFP32(UART ISP) [CX0001]  
R5F21262DFP@QFP32(UART mode) [CX3061]  
R5F21262JFP@QFP32 [CX3061]  
R5F21262JFP@QFP32(single ISP) [CX0001]  
R5F21262JFP@QFP32(single wire) [CX3061]  
R5F21262JFP@QFP32(UART ISP) [CX0001]  
R5F21262JFP@QFP32(UART mode) [CX3061]  
R5F21262KFP@QFP32 [CX3061]  
R5F21262KFP@QFP32(single ISP) [CX0001]  
R5F21262KFP@QFP32(single wire) [CX3061]  
R5F21262KFP@QFP32(UART ISP) [CX0001]  
R5F21262KFP@QFP32(UART mode) [CX3061]  
R5F21262NFP@QFP32 [CX3061]  
R5F21262NFP@QFP32(single ISP) [CX0001]  
R5F21262NFP@QFP32(single wire) [CX3061]  
R5F21262NFP@QFP32(UART ISP) [CX0001]  
R5F21262NFP@QFP32(UART mode) [CX3061]  
R5F21262SDFP@QFP32 [CX3061]  
R5F21262SDFP@QFP32(single ISP) [CX0001]  
R5F21262SDFP@QFP32(single wire) [CX3061]  
R5F21262SDFP@QFP32(UART ISP) [CX0001]  
R5F21262SDFP@QFP32(UART mode) [CX3061]  
R5F21262SJFP@QFP32 [CX3061]  
R5F21262SJFP@QFP32(single ISP) [CX0001]  
R5F21262SJFP@QFP32(single wire) [CX3061]  
R5F21262SJFP@QFP32(UART ISP) [CX0001]  
R5F21262SJFP@QFP32(UART mode) [CX3061]  
R5F21262SKFP@QFP32 [CX3061]  
R5F21262SKFP@QFP32(single ISP) [CX0001]  
R5F21262SKFP@QFP32(single wire) [CX3061]  
R5F21262SKFP@QFP32(UART ISP) [CX0001]  
R5F21262SKFP@QFP32(UART mode) [CX3061]  
R5F21262SNFP@QFP32 [CX3061]  
R5F21262SNFP@QFP32(single ISP) [CX0001]  
R5F21262SNFP@QFP32(single wire) [CX3061]  
R5F21262SNFP@QFP32(UART ISP) [CX0001]  
R5F21262SNFP@QFP32(UART mode) [CX3061]  
R5F21264DFP@QFP32 [CX3061]  
R5F21264DFP@QFP32(single ISP) [CX0001]  
R5F21264DFP@QFP32(single wire) [CX3061]  
R5F21264DFP@QFP32(UART ISP) [CX0001]  
R5F21264DFP@QFP32(UART mode) [CX3061]  
R5F21264JFP@QFP32 [CX3061]  
R5F21264JFP@QFP32(single ISP) [CX0001]  
R5F21264JFP@QFP32(single wire) [CX3061]  
R5F21264JFP@QFP32(UART ISP) [CX0001]  
R5F21264JFP@QFP32(UART mode) [CX3061]  
R5F21264KFP@QFP32 [CX3061]

R5F21264KFP@QFP32(single ISP) [CX0001]  
R5F21264KFP@QFP32(single wire) [CX3061]  
R5F21264KFP@QFP32(UART ISP) [CX0001]  
R5F21264KFP@QFP32(UART mode) [CX3061]  
R5F21264NFP@QFP32 [CX3061]  
R5F21264NFP@QFP32(single ISP) [CX0001]  
R5F21264NFP@QFP32(single wire) [CX3061]  
R5F21264NFP@QFP32(UART ISP) [CX0001]  
R5F21264NFP@QFP32(UART mode) [CX3061]  
R5F21264SDFP@QFP32 [CX3061]  
R5F21264SDFP@QFP32(single ISP) [CX0001]  
R5F21264SDFP@QFP32(single wire) [CX3061]  
R5F21264SDFP@QFP32(UART ISP) [CX0001]  
R5F21264SDFP@QFP32(UART mode) [CX3061]  
R5F21264SJFP@QFP32 [CX3061]  
R5F21264SJFP@QFP32(single ISP) [CX0001]  
R5F21264SJFP@QFP32(single wire) [CX3061]  
R5F21264SJFP@QFP32(UART ISP) [CX0001]  
R5F21264SJFP@QFP32(UART mode) [CX3061]  
R5F21264SKFP@QFP32 [CX3061]  
R5F21264SKFP@QFP32(single ISP) [CX0001]  
R5F21264SKFP@QFP32(single wire) [CX3061]  
R5F21264SKFP@QFP32(UART ISP) [CX0001]  
R5F21264SKFP@QFP32(UART mode) [CX3061]  
R5F21264SNFP@QFP32 [CX3061]  
R5F21264SNFP@QFP32(single ISP) [CX0001]  
R5F21264SNFP@QFP32(single wire) [CX3061]  
R5F21264SNFP@QFP32(UART ISP) [CX0001]  
R5F21264SNFP@QFP32(UART mode) [CX3061]  
R5F21265DFP@QFP32 [CX3061]  
R5F21265DFP@QFP32(single ISP) [CX0001]  
R5F21265DFP@QFP32(single wire) [CX3061]  
R5F21265DFP@QFP32(UART ISP) [CX0001]  
R5F21265DFP@QFP32(UART mode) [CX3061]  
R5F21265JFP@QFP32 [CX3061]  
R5F21265JFP@QFP32(single ISP) [CX0001]  
R5F21265JFP@QFP32(single wire) [CX3061]  
R5F21265JFP@QFP32(UART ISP) [CX0001]  
R5F21265JFP@QFP32(UART mode) [CX3061]  
R5F21265KFP@QFP32 [CX3061]  
R5F21265KFP@QFP32(single ISP) [CX0001]  
R5F21265KFP@QFP32(single wire) [CX3061]  
R5F21265KFP@QFP32(UART ISP) [CX0001]  
R5F21265KFP@QFP32(UART mode) [CX3061]  
R5F21265NFP@QFP32 [CX3061]  
R5F21265NFP@QFP32(single ISP) [CX0001]  
R5F21265NFP@QFP32(single wire) [CX3061]  
R5F21265NFP@QFP32(UART ISP) [CX0001]  
R5F21265NFP@QFP32(UART mode) [CX3061]  
R5F21265SDFP@QFP32 [CX3061]  
R5F21265SDFP@QFP32(single ISP) [CX0001]  
R5F21265SDFP@QFP32(single wire) [CX3061]  
R5F21265SDFP@QFP32(UART ISP) [CX0001]  
R5F21265SDFP@QFP32(UART mode) [CX3061]  
R5F21265SJFP@QFP32 [CX3061]  
R5F21265SJFP@QFP32(single ISP) [CX0001]  
R5F21265SJFP@QFP32(single wire) [CX3061]  
R5F21265SJFP@QFP32(UART ISP) [CX0001]  
R5F21265SJFP@QFP32(UART mode) [CX3061]

R5F21265SKFP@QFP32 [CX3061]  
R5F21265SKFP@QFP32(single ISP) [CX0001]  
R5F21265SKFP@QFP32(single wire) [CX3061]  
R5F21265SKFP@QFP32(UART ISP) [CX0001]  
R5F21265SKFP@QFP32(UART mode) [CX3061]  
R5F21265SNFP@QFP32 [CX3061]  
R5F21265SNFP@QFP32(single ISP) [CX0001]  
R5F21265SNFP@QFP32(single wire) [CX3061]  
R5F21265SNFP@QFP32(UART ISP) [CX0001]  
R5F21265SNFP@QFP32(UART mode) [CX3061]  
R5F21266DFP@QFP32 [CX3061]  
R5F21266DFP@QFP32(single ISP) [CX0001]  
R5F21266DFP@QFP32(single wire) [CX3061]  
R5F21266DFP@QFP32(UART ISP) [CX0001]  
R5F21266DFP@QFP32(UART mode) [CX3061]  
R5F21266JFP@QFP32 [CX3061]  
R5F21266JFP@QFP32(single ISP) [CX0001]  
R5F21266JFP@QFP32(single wire) [CX3061]  
R5F21266JFP@QFP32(UART ISP) [CX0001]  
R5F21266JFP@QFP32(UART mode) [CX3061]  
R5F21266KFP@QFP32 [CX3061]  
R5F21266KFP@QFP32(single ISP) [CX0001]  
R5F21266KFP@QFP32(single wire) [CX3061]  
R5F21266KFP@QFP32(UART ISP) [CX0001]  
R5F21266KFP@QFP32(UART mode) [CX3061]  
R5F21266NFP@QFP32 [CX3061]  
R5F21266NFP@QFP32(single ISP) [CX0001]  
R5F21266NFP@QFP32(single wire) [CX3061]  
R5F21266NFP@QFP32(UART ISP) [CX0001]  
R5F21266NFP@QFP32(UART mode) [CX3061]  
R5F21266SDFP@QFP32 [CX3061]  
R5F21266SDFP@QFP32(single ISP) [CX0001]  
R5F21266SDFP@QFP32(single wire) [CX3061]  
R5F21266SDFP@QFP32(UART ISP) [CX0001]  
R5F21266SDFP@QFP32(UART mode) [CX3061]  
R5F21266SJFP@QFP32 [CX3061]  
R5F21266SJFP@QFP32(single ISP) [CX0001]  
R5F21266SJFP@QFP32(single wire) [CX3061]  
R5F21266SJFP@QFP32(UART ISP) [CX0001]  
R5F21266SJFP@QFP32(UART mode) [CX3061]  
R5F21266SKFP@QFP32 [CX3061]  
R5F21266SKFP@QFP32(single ISP) [CX0001]  
R5F21266SKFP@QFP32(single wire) [CX3061]  
R5F21266SKFP@QFP32(UART ISP) [CX0001]  
R5F21266SKFP@QFP32(UART mode) [CX3061]  
R5F21266SNFP@QFP32 [CX3061]  
R5F21266SNFP@QFP32(single ISP) [CX0001]  
R5F21266SNFP@QFP32(single wire) [CX3061]  
R5F21266SNFP@QFP32(UART ISP) [CX0001]  
R5F21266SNFP@QFP32(UART mode) [CX3061]  
R5F21272DFP@QFP32 [CX3061]  
R5F21272DFP@QFP32(single ISP) [CX0001]  
R5F21272DFP@QFP32(single wire) [CX3061]  
R5F21272DFP@QFP32(UART ISP) [CX0001]  
R5F21272DFP@QFP32(UART mode) [CX3061]  
R5F21272JFP@QFP32 [CX3061]  
R5F21272JFP@QFP32(single ISP) [CX0001]  
R5F21272JFP@QFP32(single wire) [CX3061]  
R5F21272JFP@QFP32(UART ISP) [CX0001]

R5F21272JFP@QFP32(UART mode) [CX3061]  
R5F21272KFP@QFP32 [CX3061]  
R5F21272KFP@QFP32(single ISP) [CX0001]  
R5F21272KFP@QFP32(single wire) [CX3061]  
R5F21272KFP@QFP32(UART ISP) [CX0001]  
R5F21272KFP@QFP32(UART mode) [CX3061]  
R5F21272NFP@QFP32 [CX3061]  
R5F21272NFP@QFP32(single ISP) [CX0001]  
R5F21272NFP@QFP32(single wire) [CX3061]  
R5F21272NFP@QFP32(UART ISP) [CX0001]  
R5F21272NFP@QFP32(UART mode) [CX3061]  
R5F21272SDFP@QFP32 [CX3061]  
R5F21272SDFP@QFP32(single ISP) [CX0001]  
R5F21272SDFP@QFP32(single wire) [CX3061]  
R5F21272SDFP@QFP32(UART ISP) [CX0001]  
R5F21272SDFP@QFP32(UART mode) [CX3061]  
R5F21272SJFP@QFP32 [CX3061]  
R5F21272SJFP@QFP32(single ISP) [CX0001]  
R5F21272SJFP@QFP32(single wire) [CX3061]  
R5F21272SJFP@QFP32(UART ISP) [CX0001]  
R5F21272SJFP@QFP32(UART mode) [CX3061]  
R5F21272SKFP@QFP32 [CX3061]  
R5F21272SKFP@QFP32(single ISP) [CX0001]  
R5F21272SKFP@QFP32(single wire) [CX3061]  
R5F21272SKFP@QFP32(UART ISP) [CX0001]  
R5F21272SKFP@QFP32(UART mode) [CX3061]  
R5F21272SNFP@QFP32 [CX3061]  
R5F21272SNFP@QFP32(single ISP) [CX0001]  
R5F21272SNFP@QFP32(single wire) [CX3061]  
R5F21272SNFP@QFP32(UART ISP) [CX0001]  
R5F21272SNFP@QFP32(UART mode) [CX3061]  
R5F21274DFP@QFP32 [CX3061]  
R5F21274DFP@QFP32(single ISP) [CX0001]  
R5F21274DFP@QFP32(single wire) [CX3061]  
R5F21274DFP@QFP32(UART ISP) [CX0001]  
R5F21274DFP@QFP32(UART mode) [CX3061]  
R5F21274JFP@QFP32 [CX3061]  
R5F21274JFP@QFP32(single ISP) [CX0001]  
R5F21274JFP@QFP32(single wire) [CX3061]  
R5F21274JFP@QFP32(UART ISP) [CX0001]  
R5F21274JFP@QFP32(UART mode) [CX3061]  
R5F21274KFP@QFP32 [CX3061]  
R5F21274KFP@QFP32(single ISP) [CX0001]  
R5F21274KFP@QFP32(single wire) [CX3061]  
R5F21274KFP@QFP32(UART ISP) [CX0001]  
R5F21274KFP@QFP32(UART mode) [CX3061]  
R5F21274NFP@QFP32 [CX3061]  
R5F21274NFP@QFP32(single ISP) [CX0001]  
R5F21274NFP@QFP32(single wire) [CX3061]  
R5F21274NFP@QFP32(UART ISP) [CX0001]  
R5F21274NFP@QFP32(UART mode) [CX3061]  
R5F21274SDFP@QFP32 [CX3061]  
R5F21274SDFP@QFP32(single ISP) [CX0001]  
R5F21274SDFP@QFP32(single wire) [CX3061]  
R5F21274SDFP@QFP32(UART ISP) [CX0001]  
R5F21274SDFP@QFP32(UART mode) [CX3061]  
R5F21274SJFP@QFP32 [CX3061]  
R5F21274SJFP@QFP32(single ISP) [CX0001]  
R5F21274SJFP@QFP32(single wire) [CX3061]



R5F21274SJFP@QFP32(UART ISP) [CX0001]  
R5F21274SJFP@QFP32(UART mode) [CX3061]  
R5F21274SKFP@QFP32 [CX3061]  
R5F21274SKFP@QFP32(single ISP) [CX0001]  
R5F21274SKFP@QFP32(single wire) [CX3061]  
R5F21274SKFP@QFP32(UART ISP) [CX0001]  
R5F21274SKFP@QFP32(UART mode) [CX3061]  
R5F21274SNFP@QFP32 [CX3061]  
R5F21274SNFP@QFP32(single ISP) [CX0001]  
R5F21274SNFP@QFP32(single wire) [CX3061]  
R5F21274SNFP@QFP32(UART ISP) [CX0001]  
R5F21274SNFP@QFP32(UART mode) [CX3061]  
R5F21275DFP@QFP32 [CX3061]  
R5F21275DFP@QFP32(single ISP) [CX0001]  
R5F21275DFP@QFP32(single wire) [CX3061]  
R5F21275DFP@QFP32(UART ISP) [CX0001]  
R5F21275DFP@QFP32(UART mode) [CX3061]  
R5F21275JFP@QFP32 [CX3061]  
R5F21275JFP@QFP32(single ISP) [CX0001]  
R5F21275JFP@QFP32(single wire) [CX3061]  
R5F21275JFP@QFP32(UART ISP) [CX0001]  
R5F21275JFP@QFP32(UART mode) [CX3061]  
R5F21275KFP@QFP32 [CX3061]  
R5F21275KFP@QFP32(single ISP) [CX0001]  
R5F21275KFP@QFP32(single wire) [CX3061]  
R5F21275KFP@QFP32(UART ISP) [CX0001]  
R5F21275KFP@QFP32(UART mode) [CX3061]  
R5F21275NFP@QFP32 [CX3061]  
R5F21275NFP@QFP32(single ISP) [CX0001]  
R5F21275NFP@QFP32(single wire) [CX3061]  
R5F21275NFP@QFP32(UART ISP) [CX0001]  
R5F21275NFP@QFP32(UART mode) [CX3061]  
R5F21275SDFP@QFP32 [CX3061]  
R5F21275SDFP@QFP32(single ISP) [CX0001]  
R5F21275SDFP@QFP32(single wire) [CX3061]  
R5F21275SDFP@QFP32(UART ISP) [CX0001]  
R5F21275SDFP@QFP32(UART mode) [CX3061]  
R5F21275SJFP@QFP32 [CX3061]  
R5F21275SJFP@QFP32(single ISP) [CX0001]  
R5F21275SJFP@QFP32(single wire) [CX3061]  
R5F21275SJFP@QFP32(UART ISP) [CX0001]  
R5F21275SJFP@QFP32(UART mode) [CX3061]  
R5F21275SKFP@QFP32 [CX3061]  
R5F21275SKFP@QFP32(single ISP) [CX0001]  
R5F21275SKFP@QFP32(single wire) [CX3061]  
R5F21275SKFP@QFP32(UART ISP) [CX0001]  
R5F21275SKFP@QFP32(UART mode) [CX3061]  
R5F21275SNFP@QFP32 [CX3061]  
R5F21275SNFP@QFP32(single ISP) [CX0001]  
R5F21275SNFP@QFP32(single wire) [CX3061]  
R5F21275SNFP@QFP32(UART ISP) [CX0001]  
R5F21275SNFP@QFP32(UART mode) [CX3061]  
R5F21276DFP@QFP32 [CX3061]  
R5F21276DFP@QFP32(single ISP) [CX0001]  
R5F21276DFP@QFP32(single wire) [CX3061]  
R5F21276DFP@QFP32(UART ISP) [CX0001]  
R5F21276DFP@QFP32(UART mode) [CX3061]  
R5F21276JFP@QFP32 [CX3061]  
R5F21276JFP@QFP32(single ISP) [CX0001]

R5F21276JFP@QFP32(single wire) [CX3061]  
R5F21276JFP@QFP32(UART ISP) [CX0001]  
R5F21276JFP@QFP32(UART mode) [CX3061]  
R5F21276KFP@QFP32 [CX3061]  
R5F21276KFP@QFP32(single ISP) [CX0001]  
R5F21276KFP@QFP32(single wire) [CX3061]  
R5F21276KFP@QFP32(UART ISP) [CX0001]  
R5F21276KFP@QFP32(UART mode) [CX3061]  
R5F21276NFP@QFP32 [CX3061]  
R5F21276NFP@QFP32(single ISP) [CX0001]  
R5F21276NFP@QFP32(single wire) [CX3061]  
R5F21276NFP@QFP32(UART ISP) [CX0001]  
R5F21276NFP@QFP32(UART mode) [CX3061]  
R5F21276SDFP@QFP32 [CX3061]  
R5F21276SDFP@QFP32(single ISP) [CX0001]  
R5F21276SDFP@QFP32(single wire) [CX3061]  
R5F21276SDFP@QFP32(UART ISP) [CX0001]  
R5F21276SDFP@QFP32(UART mode) [CX3061]  
R5F21276SJFP@QFP32 [CX3061]  
R5F21276SJFP@QFP32(single ISP) [CX0001]  
R5F21276SJFP@QFP32(single wire) [CX3061]  
R5F21276SJFP@QFP32(UART ISP) [CX0001]  
R5F21276SJFP@QFP32(UART mode) [CX3061]  
R5F21276SKFP@QFP32 [CX3061]  
R5F21276SKFP@QFP32(single ISP) [CX0001]  
R5F21276SKFP@QFP32(single wire) [CX3061]  
R5F21276SKFP@QFP32(UART ISP) [CX0001]  
R5F21276SKFP@QFP32(UART mode) [CX3061]  
R5F21276SNFP@QFP32 [CX3061]  
R5F21276SNFP@QFP32(single ISP) [CX0001]  
R5F21276SNFP@QFP32(single wire) [CX3061]  
R5F21276SNFP@QFP32(UART ISP) [CX0001]  
R5F21276SNFP@QFP32(UART mode) [CX3061]  
R5F21282DSP@SOIC20 [CX1000]  
R5F21282DSP@SOIC20(single ISP) [CX0001]  
R5F21282DSP@SOIC20(single wire) [CX1000]  
R5F21282DSP@SOIC20(UART ISP) [CX0001]  
R5F21282DSP@SOIC20(UART mode) [CX1000]  
R5F21282JSP@SOIC20 [CX1000]  
R5F21282JSP@SOIC20(single ISP) [CX0001]  
R5F21282JSP@SOIC20(single wire) [CX1000]  
R5F21282JSP@SOIC20(UART ISP) [CX0001]  
R5F21282JSP@SOIC20(UART mode) [CX1000]  
R5F21282KSP@SOIC20 [CX1000]  
R5F21282KSP@SOIC20(single ISP) [CX0001]  
R5F21282KSP@SOIC20(single wire) [CX1000]  
R5F21282KSP@SOIC20(UART ISP) [CX0001]  
R5F21282KSP@SOIC20(UART mode) [CX1000]  
R5F21282NSP@SOIC20 [CX1000]  
R5F21282NSP@SOIC20(single ISP) [CX0001]  
R5F21282NSP@SOIC20(single wire) [CX1000]  
R5F21282NSP@SOIC20(UART ISP) [CX0001]  
R5F21282NSP@SOIC20(UART mode) [CX1000]  
R5F21282SDSP@SOIC20 [CX1000]  
R5F21282SDSP@SOIC20(single ISP) [CX0001]  
R5F21282SDSP@SOIC20(single wire) [CX1000]  
R5F21282SDSP@SOIC20(UART ISP) [CX0001]  
R5F21282SDSP@SOIC20(UART mode) [CX1000]  
R5F21282SJSP@SOIC20 [CX1000]

R5F21282SJSP@SOIC20(single ISP) [CX0001]  
R5F21282SJSP@SOIC20(single wire) [CX1000]  
R5F21282SJSP@SOIC20(UART ISP) [CX0001]  
R5F21282SJSP@SOIC20(UART mode) [CX1000]  
R5F21282SKSP@SOIC20 [CX1000]  
R5F21282SKSP@SOIC20(single ISP) [CX0001]  
R5F21282SKSP@SOIC20(single wire) [CX1000]  
R5F21282SKSP@SOIC20(UART ISP) [CX0001]  
R5F21282SKSP@SOIC20(UART mode) [CX1000]  
R5F21282SNSP@SOIC20 [CX1000]  
R5F21282SNSP@SOIC20(single ISP) [CX0001]  
R5F21282SNSP@SOIC20(single wire) [CX1000]  
R5F21282SNSP@SOIC20(UART ISP) [CX0001]  
R5F21282SNSP@SOIC20(UART mode) [CX1000]  
R5F21284DSP@SOIC20 [CX1000]  
R5F21284DSP@SOIC20(single ISP) [CX0001]  
R5F21284DSP@SOIC20(single wire) [CX1000]  
R5F21284DSP@SOIC20(UART ISP) [CX0001]  
R5F21284DSP@SOIC20(UART mode) [CX1000]  
R5F21284JSP@SOIC20 [CX1000]  
R5F21284JSP@SOIC20(single ISP) [CX0001]  
R5F21284JSP@SOIC20(single wire) [CX1000]  
R5F21284JSP@SOIC20(UART ISP) [CX0001]  
R5F21284JSP@SOIC20(UART mode) [CX1000]  
R5F21284KSP@SOIC20 [CX1000]  
R5F21284KSP@SOIC20(single ISP) [CX0001]  
R5F21284KSP@SOIC20(single wire) [CX1000]  
R5F21284KSP@SOIC20(UART ISP) [CX0001]  
R5F21284KSP@SOIC20(UART mode) [CX1000]  
R5F21284NSP@SOIC20 [CX1000]  
R5F21284NSP@SOIC20(single ISP) [CX0001]  
R5F21284NSP@SOIC20(single wire) [CX1000]  
R5F21284NSP@SOIC20(UART ISP) [CX0001]  
R5F21284NSP@SOIC20(UART mode) [CX1000]  
R5F21284SDSP@SOIC20 [CX1000]  
R5F21284SDSP@SOIC20(single ISP) [CX0001]  
R5F21284SDSP@SOIC20(single wire) [CX1000]  
R5F21284SDSP@SOIC20(UART ISP) [CX0001]  
R5F21284SDSP@SOIC20(UART mode) [CX1000]  
R5F21284SJSP@SOIC20 [CX1000]  
R5F21284SJSP@SOIC20(single ISP) [CX0001]  
R5F21284SJSP@SOIC20(single wire) [CX1000]  
R5F21284SJSP@SOIC20(UART ISP) [CX0001]  
R5F21284SJSP@SOIC20(UART mode) [CX1000]  
R5F21284SKSP@SOIC20 [CX1000]  
R5F21284SKSP@SOIC20(single ISP) [CX0001]  
R5F21284SKSP@SOIC20(single wire) [CX1000]  
R5F21284SKSP@SOIC20(UART ISP) [CX0001]  
R5F21284SKSP@SOIC20(UART mode) [CX1000]  
R5F21284SNSP@SOIC20 [CX1000]  
R5F21284SNSP@SOIC20(single ISP) [CX0001]  
R5F21284SNSP@SOIC20(single wire) [CX1000]  
R5F21284SNSP@SOIC20(UART ISP) [CX0001]  
R5F21284SNSP@SOIC20(UART mode) [CX1000]  
R5F21292DSP@SOIC20 [CX1000]  
R5F21292DSP@SOIC20(single ISP) [CX0001]  
R5F21292DSP@SOIC20(single wire) [CX1000]  
R5F21292DSP@SOIC20(UART ISP) [CX0001]  
R5F21292DSP@SOIC20(UART mode) [CX1000]

R5F21292JSP@SOIC20 [CX1000]  
R5F21292JSP@SOIC20(single ISP) [CX0001]  
R5F21292JSP@SOIC20(single wire) [CX1000]  
R5F21292JSP@SOIC20(UART ISP) [CX0001]  
R5F21292JSP@SOIC20(UART mode) [CX1000]  
R5F21292KSP@SOIC20 [CX1000]  
R5F21292KSP@SOIC20(single ISP) [CX0001]  
R5F21292KSP@SOIC20(single wire) [CX1000]  
R5F21292KSP@SOIC20(UART ISP) [CX0001]  
R5F21292KSP@SOIC20(UART mode) [CX1000]  
R5F21292NSP@SOIC20 [CX1000]  
R5F21292NSP@SOIC20(single ISP) [CX0001]  
R5F21292NSP@SOIC20(single wire) [CX1000]  
R5F21292NSP@SOIC20(UART ISP) [CX0001]  
R5F21292NSP@SOIC20(UART mode) [CX1000]  
R5F21292SDSP@SOIC20 [CX1000]  
R5F21292SDSP@SOIC20(single ISP) [CX0001]  
R5F21292SDSP@SOIC20(single wire) [CX1000]  
R5F21292SDSP@SOIC20(UART ISP) [CX0001]  
R5F21292SDSP@SOIC20(UART mode) [CX1000]  
R5F21292SJSP@SOIC20 [CX1000]  
R5F21292SJSP@SOIC20(single ISP) [CX0001]  
R5F21292SJSP@SOIC20(single wire) [CX1000]  
R5F21292SJSP@SOIC20(UART ISP) [CX0001]  
R5F21292SJSP@SOIC20(UART mode) [CX1000]  
R5F21292SKSP@SOIC20 [CX1000]  
R5F21292SKSP@SOIC20(single ISP) [CX0001]  
R5F21292SKSP@SOIC20(single wire) [CX1000]  
R5F21292SKSP@SOIC20(UART ISP) [CX0001]  
R5F21292SKSP@SOIC20(UART mode) [CX1000]  
R5F21292SNSP@SOIC20 [CX1000]  
R5F21292SNSP@SOIC20(single ISP) [CX0001]  
R5F21292SNSP@SOIC20(single wire) [CX1000]  
R5F21292SNSP@SOIC20(UART ISP) [CX0001]  
R5F21292SNSP@SOIC20(UART mode) [CX1000]  
R5F21294DSP@SOIC20 [CX1000]  
R5F21294DSP@SOIC20(single ISP) [CX0001]  
R5F21294DSP@SOIC20(single wire) [CX1000]  
R5F21294DSP@SOIC20(UART ISP) [CX0001]  
R5F21294DSP@SOIC20(UART mode) [CX1000]  
R5F21294JSP@SOIC20 [CX1000]  
R5F21294JSP@SOIC20(single ISP) [CX0001]  
R5F21294JSP@SOIC20(single wire) [CX1000]  
R5F21294JSP@SOIC20(UART ISP) [CX0001]  
R5F21294JSP@SOIC20(UART mode) [CX1000]  
R5F21294KSP@SOIC20 [CX1000]  
R5F21294KSP@SOIC20(single ISP) [CX0001]  
R5F21294KSP@SOIC20(single wire) [CX1000]  
R5F21294KSP@SOIC20(UART ISP) [CX0001]  
R5F21294KSP@SOIC20(UART mode) [CX1000]  
R5F21294NSP@SOIC20 [CX1000]  
R5F21294NSP@SOIC20(single ISP) [CX0001]  
R5F21294NSP@SOIC20(single wire) [CX1000]  
R5F21294NSP@SOIC20(UART ISP) [CX0001]  
R5F21294NSP@SOIC20(UART mode) [CX1000]  
R5F21294SDSP@SOIC20 [CX1000]  
R5F21294SDSP@SOIC20(single ISP) [CX0001]  
R5F21294SDSP@SOIC20(single wire) [CX1000]  
R5F21294SDSP@SOIC20(UART ISP) [CX0001]

R5F21294SDSP@SOIC20(UART mode) [CX1000]  
R5F21294SJSP@SOIC20 [CX1000]  
R5F21294SJSP@SOIC20(single ISP) [CX0001]  
R5F21294SJSP@SOIC20(single wire) [CX1000]  
R5F21294SJSP@SOIC20(UART ISP) [CX0001]  
R5F21294SJSP@SOIC20(UART mode) [CX1000]  
R5F21294SKSP@SOIC20 [CX1000]  
R5F21294SKSP@SOIC20(single ISP) [CX0001]  
R5F21294SKSP@SOIC20(single wire) [CX1000]  
R5F21294SKSP@SOIC20(UART ISP) [CX0001]  
R5F21294SKSP@SOIC20(UART mode) [CX1000]  
R5F21294SNSP@SOIC20 [CX1000]  
R5F21294SNSP@SOIC20(single ISP) [CX0001]  
R5F21294SNSP@SOIC20(single wire) [CX1000]  
R5F21294SNSP@SOIC20(UART ISP) [CX0001]  
R5F21294SNSP@SOIC20(UART mode) [CX1000]  
R5F212A7SDFA@TQFP64 [CX3044]  
R5F212A7SDFA@TQFP64(single ISP) [CX0001]  
R5F212A7SDFA@TQFP64(single wire) [CX3013]  
R5F212A7SDFA@TQFP64(UART ISP) [CX0001]  
R5F212A7SDFA@TQFP64(UART mode) [CX3013]  
R5F212A7SDFP@TQFP64 [CX3011]  
R5F212A7SDFP@TQFP64(single ISP) [CX0001]  
R5F212A7SDFP@TQFP64(single wire) [CX3011]  
R5F212A7SDFP@TQFP64(UART ISP) [CX0001]  
R5F212A7SDFP@TQFP64(UART mode) [CX3011]  
R5F212A7SNFA@TQFP64 [CX3044]  
R5F212A7SNFA@TQFP64(single ISP) [CX0001]  
R5F212A7SNFA@TQFP64(single wire) [CX3013]  
R5F212A7SNFA@TQFP64(UART ISP) [CX0001]  
R5F212A7SNFA@TQFP64(UART mode) [CX3013]  
R5F212A7SNFP@TQFP64 [CX3011]  
R5F212A7SNFP@TQFP64(single ISP) [CX0001]  
R5F212A7SNFP@TQFP64(single wire) [CX3011]  
R5F212A7SNFP@TQFP64(UART ISP) [CX0001]  
R5F212A7SNFP@TQFP64(UART mode) [CX3011]  
R5F212A8SDFA@TQFP64 [CX3044]  
R5F212A8SDFA@TQFP64(single ISP) [CX0001]  
R5F212A8SDFA@TQFP64(single wire) [CX3013]  
R5F212A8SDFA@TQFP64(UART ISP) [CX0001]  
R5F212A8SDFA@TQFP64(UART mode) [CX3013]  
R5F212A8SDFP@TQFP64 [CX3011]  
R5F212A8SDFP@TQFP64(single ISP) [CX0001]  
R5F212A8SDFP@TQFP64(single wire) [CX3011]  
R5F212A8SDFP@TQFP64(UART ISP) [CX0001]  
R5F212A8SDFP@TQFP64(UART mode) [CX3011]  
R5F212A8SNFA@TQFP64 [CX3044]  
R5F212A8SNFA@TQFP64(single ISP) [CX0001]  
R5F212A8SNFA@TQFP64(single wire) [CX3013]  
R5F212A8SNFA@TQFP64(UART ISP) [CX0001]  
R5F212A8SNFA@TQFP64(UART mode) [CX3013]  
R5F212A8SNFP@TQFP64 [CX3011]  
R5F212A8SNFP@TQFP64(single ISP) [CX0001]  
R5F212A8SNFP@TQFP64(single wire) [CX3011]  
R5F212A8SNFP@TQFP64(UART ISP) [CX0001]  
R5F212A8SNFP@TQFP64(UART mode) [CX3011]  
R5F212AASDFA@TQFP64 [CX3044]  
R5F212AASDFA@TQFP64(single ISP) [CX0001]  
R5F212AASDFA@TQFP64(single wire) [CX3013]

R5F212AASDFA@TQFP64(UART ISP) [CX0001]  
R5F212AASDFA@TQFP64(UART mode) [CX3013]  
R5F212AASDFP@TQFP64 [CX3011]  
R5F212AASDFP@TQFP64(single ISP) [CX0001]  
R5F212AASDFP@TQFP64(single wire) [CX3011]  
R5F212AASDFP@TQFP64(UART ISP) [CX0001]  
R5F212AASDFP@TQFP64(UART mode) [CX3011]  
R5F212AASNFA@TQFP64 [CX3044]  
R5F212AASNFA@TQFP64(single ISP) [CX0001]  
R5F212AASNFA@TQFP64(single wire) [CX3013]  
R5F212AASNFA@TQFP64(UART ISP) [CX0001]  
R5F212AASNFA@TQFP64(UART mode) [CX3013]  
R5F212AASNFP@TQFP64 [CX3011]  
R5F212AASNFP@TQFP64(single ISP) [CX0001]  
R5F212AASNFP@TQFP64(single wire) [CX3011]  
R5F212AASNFP@TQFP64(UART ISP) [CX0001]  
R5F212AASNFP@TQFP64(UART mode) [CX3011]  
R5F212ACSDFA@TQFP64 [CX3044]  
R5F212ACSDFA@TQFP64(single ISP) [CX0001]  
R5F212ACSDFA@TQFP64(single wire) [CX3013]  
R5F212ACSDFA@TQFP64(UART ISP) [CX0001]  
R5F212ACSDFA@TQFP64(UART mode) [CX3013]  
R5F212ACSDFP@TQFP64 [CX3011]  
R5F212ACSDFP@TQFP64(single ISP) [CX0001]  
R5F212ACSDFP@TQFP64(single wire) [CX3011]  
R5F212ACSDFP@TQFP64(UART ISP) [CX0001]  
R5F212ACSDFP@TQFP64(UART mode) [CX3011]  
R5F212ACSNFA@TQFP64 [CX3044]  
R5F212ACSNFA@TQFP64(single ISP) [CX0001]  
R5F212ACSNFA@TQFP64(single wire) [CX3013]  
R5F212ACSNFA@TQFP64(UART ISP) [CX0001]  
R5F212ACSNFA@TQFP64(UART mode) [CX3013]  
R5F212ACSNFP@TQFP64 [CX3011]  
R5F212ACSNFP@TQFP64(single ISP) [CX0001]  
R5F212ACSNFP@TQFP64(single wire) [CX3011]  
R5F212ACSNFP@TQFP64(UART ISP) [CX0001]  
R5F212ACSNFP@TQFP64(UART mode) [CX3011]  
R5F212B7SDFA@TQFP64 [CX3044]  
R5F212B7SDFA@TQFP64(single ISP) [CX0001]  
R5F212B7SDFA@TQFP64(single wire) [CX3013]  
R5F212B7SDFA@TQFP64(UART ISP) [CX0001]  
R5F212B7SDFA@TQFP64(UART mode) [CX3013]  
R5F212B7SDFP@TQFP64 [CX3011]  
R5F212B7SDFP@TQFP64(single ISP) [CX0001]  
R5F212B7SDFP@TQFP64(single wire) [CX3011]  
R5F212B7SDFP@TQFP64(UART ISP) [CX0001]  
R5F212B7SDFP@TQFP64(UART mode) [CX3011]  
R5F212B7SNFA@TQFP64 [CX3044]  
R5F212B7SNFA@TQFP64(single ISP) [CX0001]  
R5F212B7SNFA@TQFP64(single wire) [CX3013]  
R5F212B7SNFA@TQFP64(UART ISP) [CX0001]  
R5F212B7SNFA@TQFP64(UART mode) [CX3013]  
R5F212B7SNFP@TQFP64 [CX3011]  
R5F212B7SNFP@TQFP64(single ISP) [CX0001]  
R5F212B7SNFP@TQFP64(single wire) [CX3011]  
R5F212B7SNFP@TQFP64(UART ISP) [CX0001]  
R5F212B7SNFP@TQFP64(UART mode) [CX3011]  
R5F212B8SDFA@TQFP64 [CX3044]  
R5F212B8SDFA@TQFP64(single ISP) [CX0001]

R5F212B8SDFA@TQFP64(single wire) [CX3013]  
R5F212B8SDFA@TQFP64(UART ISP) [CX0001]  
R5F212B8SDFA@TQFP64(UART mode) [CX3013]  
R5F212B8SDFP@TQFP64 [CX3011]  
R5F212B8SDFP@TQFP64(single ISP) [CX0001]  
R5F212B8SDFP@TQFP64(single wire) [CX3011]  
R5F212B8SDFP@TQFP64(UART ISP) [CX0001]  
R5F212B8SDFP@TQFP64(UART mode) [CX3011]  
R5F212B8SNFA@TQFP64 [CX3044]  
R5F212B8SNFA@TQFP64(single ISP) [CX0001]  
R5F212B8SNFA@TQFP64(single wire) [CX3013]  
R5F212B8SNFA@TQFP64(UART ISP) [CX0001]  
R5F212B8SNFA@TQFP64(UART mode) [CX3013]  
R5F212B8SNFP@TQFP64 [CX3011]  
R5F212B8SNFP@TQFP64(single ISP) [CX0001]  
R5F212B8SNFP@TQFP64(single wire) [CX3011]  
R5F212B8SNFP@TQFP64(UART ISP) [CX0001]  
R5F212B8SNFP@TQFP64(UART mode) [CX3011]  
R5F212BASDFA@TQFP64 [CX3044]  
R5F212BASDFA@TQFP64(single ISP) [CX0001]  
R5F212BASDFA@TQFP64(single wire) [CX3013]  
R5F212BASDFA@TQFP64(UART ISP) [CX0001]  
R5F212BASDFA@TQFP64(UART mode) [CX3013]  
R5F212BASDFP@TQFP64 [CX3011]  
R5F212BASDFP@TQFP64(single ISP) [CX0001]  
R5F212BASDFP@TQFP64(single wire) [CX3011]  
R5F212BASDFP@TQFP64(UART ISP) [CX0001]  
R5F212BASDFP@TQFP64(UART mode) [CX3011]  
R5F212BASNFA@TQFP64 [CX3044]  
R5F212BASNFA@TQFP64(single ISP) [CX0001]  
R5F212BASNFA@TQFP64(single wire) [CX3013]  
R5F212BASNFA@TQFP64(UART ISP) [CX0001]  
R5F212BASNFA@TQFP64(UART mode) [CX3013]  
R5F212BASNFP@TQFP64 [CX3011]  
R5F212BASNFP@TQFP64(single ISP) [CX0001]  
R5F212BASNFP@TQFP64(single wire) [CX3011]  
R5F212BASNFP@TQFP64(UART ISP) [CX0001]  
R5F212BASNFP@TQFP64(UART mode) [CX3011]  
R5F212BCSDFA@TQFP64 [CX3044]  
R5F212BCSDFA@TQFP64(single ISP) [CX0001]  
R5F212BCSDFA@TQFP64(single wire) [CX3013]  
R5F212BCSDFA@TQFP64(UART ISP) [CX0001]  
R5F212BCSDFA@TQFP64(UART mode) [CX3013]  
R5F212BCSDFP@TQFP64 [CX3011]  
R5F212BCSDFP@TQFP64(single ISP) [CX0001]  
R5F212BCSDFP@TQFP64(single wire) [CX3011]  
R5F212BCSDFP@TQFP64(UART ISP) [CX0001]  
R5F212BCSDFP@TQFP64(UART mode) [CX3011]  
R5F212BCSNFA@TQFP64 [CX3044]  
R5F212BCSNFA@TQFP64(single ISP) [CX0001]  
R5F212BCSNFA@TQFP64(single wire) [CX3013]  
R5F212BCSNFA@TQFP64(UART ISP) [CX0001]  
R5F212BCSNFA@TQFP64(UART mode) [CX3013]  
R5F212BCSNFP@TQFP64 [CX3011]  
R5F212BCSNFP@TQFP64(single ISP) [CX0001]  
R5F212BCSNFP@TQFP64(single wire) [CX3011]  
R5F212BCSNFP@TQFP64(UART ISP) [CX0001]  
R5F212BCSNFP@TQFP64(UART mode) [CX3011]  
R5F212C7SDFP@TQFP80 [CX3016]

R5F212C7SDFP@TQFP80(single ISP) [CX0001]  
R5F212C7SDFP@TQFP80(single wire) [CX3016]  
R5F212C7SDFP@TQFP80(UART ISP) [CX0001]  
R5F212C7SDFP@TQFP80(UART mode) [CX3016]  
R5F212C7SNFP@TQFP80 [CX3016]  
R5F212C7SNFP@TQFP80(single ISP) [CX0001]  
R5F212C7SNFP@TQFP80(single wire) [CX3016]  
R5F212C7SNFP@TQFP80(UART ISP) [CX0001]  
R5F212C7SNFP@TQFP80(UART mode) [CX3016]  
R5F212C8SDFP@TQFP80 [CX3016]  
R5F212C8SDFP@TQFP80(single ISP) [CX0001]  
R5F212C8SDFP@TQFP80(single wire) [CX3016]  
R5F212C8SDFP@TQFP80(UART ISP) [CX0001]  
R5F212C8SDFP@TQFP80(UART mode) [CX3016]  
R5F212C8SNFP@TQFP80 [CX3016]  
R5F212C8SNFP@TQFP80(single ISP) [CX0001]  
R5F212C8SNFP@TQFP80(single wire) [CX3016]  
R5F212C8SNFP@TQFP80(UART ISP) [CX0001]  
R5F212C8SNFP@TQFP80(UART mode) [CX3016]  
R5F212CASDFP@TQFP80 [CX3016]  
R5F212CASDFP@TQFP80(single ISP) [CX0001]  
R5F212CASDFP@TQFP80(single wire) [CX3016]  
R5F212CASDFP@TQFP80(UART ISP) [CX0001]  
R5F212CASDFP@TQFP80(UART mode) [CX3016]  
R5F212CASNFP@TQFP80 [CX3016]  
R5F212CASNFP@TQFP80(single ISP) [CX0001]  
R5F212CASNFP@TQFP80(single wire) [CX3016]  
R5F212CASNFP@TQFP80(UART ISP) [CX0001]  
R5F212CASNFP@TQFP80(UART mode) [CX3016]  
R5F212CCSDFP@TQFP80 [CX3016]  
R5F212CCSDFP@TQFP80(single ISP) [CX0001]  
R5F212CCSDFP@TQFP80(single wire) [CX3016]  
R5F212CCSDFP@TQFP80(UART ISP) [CX0001]  
R5F212CCSDFP@TQFP80(UART mode) [CX3016]  
R5F212CCSNFP@TQFP80 [CX3016]  
R5F212CCSNFP@TQFP80(single ISP) [CX0001]  
R5F212CCSNFP@TQFP80(single wire) [CX3016]  
R5F212CCSNFP@TQFP80(UART ISP) [CX0001]  
R5F212CCSNFP@TQFP80(UART mode) [CX3016]  
R5F212D7SDFP@TQFP80 [CX3016]  
R5F212D7SDFP@TQFP80(single ISP) [CX0001]  
R5F212D7SDFP@TQFP80(single wire) [CX3016]  
R5F212D7SDFP@TQFP80(UART ISP) [CX0001]  
R5F212D7SDFP@TQFP80(UART mode) [CX3016]  
R5F212D7SNFP@TQFP80 [CX3016]  
R5F212D7SNFP@TQFP80(single ISP) [CX0001]  
R5F212D7SNFP@TQFP80(single wire) [CX3016]  
R5F212D7SNFP@TQFP80(UART ISP) [CX0001]  
R5F212D7SNFP@TQFP80(UART mode) [CX3016]  
R5F212D8SDFP@TQFP80 [CX3016]  
R5F212D8SDFP@TQFP80(single ISP) [CX0001]  
R5F212D8SDFP@TQFP80(single wire) [CX3016]  
R5F212D8SDFP@TQFP80(UART ISP) [CX0001]  
R5F212D8SDFP@TQFP80(UART mode) [CX3016]  
R5F212D8SNFP@TQFP80 [CX3016]  
R5F212D8SNFP@TQFP80(single ISP) [CX0001]  
R5F212D8SNFP@TQFP80(single wire) [CX3016]  
R5F212D8SNFP@TQFP80(UART ISP) [CX0001]  
R5F212D8SNFP@TQFP80(UART mode) [CX3016]



R5F212DASDFP@TQFP80 [CX3016]  
R5F212DASDFP@TQFP80(single ISP) [CX0001]  
R5F212DASDFP@TQFP80(single wire) [CX3016]  
R5F212DASDFP@TQFP80(UART ISP) [CX0001]  
R5F212DASDFP@TQFP80(UART mode) [CX3016]  
R5F212DASNFP@TQFP80 [CX3016]  
R5F212DASNFP@TQFP80(single ISP) [CX0001]  
R5F212DASNFP@TQFP80(single wire) [CX3016]  
R5F212DASNFP@TQFP80(UART ISP) [CX0001]  
R5F212DASNFP@TQFP80(UART mode) [CX3016]  
R5F212DCSDFP@TQFP80 [CX3016]  
R5F212DCSDFP@TQFP80(single ISP) [CX0001]  
R5F212DCSDFP@TQFP80(single wire) [CX3016]  
R5F212DCSDFP@TQFP80(UART ISP) [CX0001]  
R5F212DCSDFP@TQFP80(UART mode) [CX3016]  
R5F212DCSNFP@TQFP80 [CX3016]  
R5F212DCSNFP@TQFP80(single ISP) [CX0001]  
R5F212DCSNFP@TQFP80(single wire) [CX3016]  
R5F212DCSNFP@TQFP80(UART ISP) [CX0001]  
R5F212DCSNFP@TQFP80(UART mode) [CX3016]  
R5F212G4SDFP@QFP32 [CX3061]  
R5F212G4SDFP@QFP32(single ISP) [CX0001]  
R5F212G4SDFP@QFP32(single wire) [CX3061]  
R5F212G4SNFP@QFP32 [CX3061]  
R5F212G4SNFP@QFP32(single ISP) [CX0001]  
R5F212G4SNFP@QFP32(single wire) [CX3061]  
R5F212G5SDFP@QFP32 [CX3061]  
R5F212G5SDFP@QFP32(single ISP) [CX0001]  
R5F212G5SDFP@QFP32(single wire) [CX3061]  
R5F212G5SNFP@QFP32 [CX3061]  
R5F212G5SNFP@QFP32(single ISP) [CX0001]  
R5F212G5SNFP@QFP32(single wire) [CX3061]  
R5F212G6SDFP@QFP32 [CX3061]  
R5F212G6SDFP@QFP32(single ISP) [CX0001]  
R5F212G6SDFP@QFP32(single wire) [CX3061]  
R5F212G6SNFP@QFP32 [CX3061]  
R5F212G6SNFP@QFP32(single ISP) [CX0001]  
R5F212G6SNFP@QFP32(single wire) [CX3061]  
R5F212H1SDSP@TSSOP20 [CX1000]  
R5F212H1SDSP@TSSOP20(single ISP) [CX0001]  
R5F212H1SDSP@TSSOP20(single) [CX1000]  
R5F212H1SNSP@TSSOP20 [CX1000]  
R5F212H1SNSP@TSSOP20(single ISP) [CX0001]  
R5F212H1SNSP@TSSOP20(single) [CX1000]  
R5F212H2SDSP@TSSOP20 [CX1000]  
R5F212H2SDSP@TSSOP20(single ISP) [CX0001]  
R5F212H2SDSP@TSSOP20(single) [CX1000]  
R5F212H2SNSP@TSSOP20 [CX1000]  
R5F212H2SNSP@TSSOP20(single ISP) [CX0001]  
R5F212H2SNSP@TSSOP20(single) [CX1000]  
R5F212J0SDSP@TSSOP20 [CX1000]  
R5F212J0SDSP@TSSOP20(single ISP) [CX0001]  
R5F212J0SDSP@TSSOP20(single) [CX1000]  
R5F212J0SNSP@TSSOP20 [CX1000]  
R5F212J0SNSP@TSSOP20(single ISP) [CX0001]  
R5F212J0SNSP@TSSOP20(single) [CX1000]  
R5F212J1SDSP@TSSOP20 [CX1000]  
R5F212J1SDSP@TSSOP20(single ISP) [CX0001]  
R5F212J1SDSP@TSSOP20(single) [CX1000]

R5F212J1SNSP@TSSOP20 [CX1000]  
R5F212J1SNSP@TSSOP20(single ISP) [CX0001]  
R5F212J1SNSP@TSSOP20(single) [CX1000]  
R5F212K2SDFP@QFP32 [CX3061]  
R5F212K2SDFP@QFP32(single ISP) [CX0001]  
R5F212K2SDFP@QFP32(single wire) [CX3050]  
R5F212K2SDFP@QFP32(UART ISP) [CX0001]  
R5F212K2SDFP@QFP32(UART mode) [CX3050]  
R5F212K2SNFP@QFP32 [CX3061]  
R5F212K2SNFP@QFP32(single ISP) [CX0001]  
R5F212K2SNFP@QFP32(single wire) [CX3050]  
R5F212K2SNFP@QFP32(UART ISP) [CX0001]  
R5F212K2SNFP@QFP32(UART mode) [CX3050]  
R5F212K4SDFP@QFP32 [CX3061]  
R5F212K4SDFP@QFP32(single ISP) [CX0001]  
R5F212K4SDFP@QFP32(single wire) [CX3050]  
R5F212K4SDFP@QFP32(UART ISP) [CX0001]  
R5F212K4SDFP@QFP32(UART mode) [CX3050]  
R5F212K4SNFP@QFP32 [CX3061]  
R5F212K4SNFP@QFP32(single ISP) [CX0001]  
R5F212K4SNFP@QFP32(single wire) [CX3050]  
R5F212K4SNFP@QFP32(UART ISP) [CX0001]  
R5F212K4SNFP@QFP32(UART mode) [CX3050]  
R5F212L2SDFP@QFP32 [CX3061]  
R5F212L2SDFP@QFP32(single ISP) [CX0001]  
R5F212L2SDFP@QFP32(single wire) [CX3050]  
R5F212L2SDFP@QFP32(UART ISP) [CX0001]  
R5F212L2SDFP@QFP32(UART mode) [CX3050]  
R5F212L2SNFP@QFP32 [CX3061]  
R5F212L2SNFP@QFP32(single ISP) [CX0001]  
R5F212L2SNFP@QFP32(single wire) [CX3050]  
R5F212L2SNFP@QFP32(UART ISP) [CX0001]  
R5F212L2SNFP@QFP32(UART mode) [CX3050]  
R5F212L4SDFP@QFP32 [CX3061]  
R5F212L4SDFP@QFP32(single ISP) [CX0001]  
R5F212L4SDFP@QFP32(single wire) [CX3050]  
R5F212L4SDFP@QFP32(UART ISP) [CX0001]  
R5F212L4SDFP@QFP32(UART mode) [CX3050]  
R5F212L4SNFP@QFP32 [CX3061]  
R5F212L4SNFP@QFP32(single ISP) [CX0001]  
R5F212L4SNFP@QFP32(single wire) [CX3050]  
R5F212L4SNFP@QFP32(UART ISP) [CX0001]  
R5F212L4SNFP@QFP32(UART mode) [CX3050]  
R5F21331ADFP [CX3001] R5F21331ANFP [CX3001]  
R5F21331CDFP [CX3001] R5F21331CNFP [CX3001]  
R5F21331DDFP [CX3001] R5F21331DNFP [CX3001]  
R5F21331MDFP [CX3001] R5F21331MNFP [CX3001]  
R5F21332ADFP [CX3001] R5F21332ANFP [CX3001]  
R5F21332CDFP [CX3001] R5F21332CNFP [CX3001]  
R5F21332DDFP [CX3001] R5F21332DNFP [CX3001]  
R5F21332MDFP [CX3001] R5F21332MNFP [CX3001]  
R5F21334ADFP [CX3001] R5F21334ANFP [CX3001]  
R5F21334CDFP [CX3001] R5F21334CNFP [CX3001]  
R5F21334DDFP [CX3001] R5F21334DNFP [CX3001]  
R5F21334MDFP [CX3001] R5F21334MNFP [CX3001]  
R5F21334TDFP [CX3001] R5F21334TNFP [CX3001]  
R5F21335ADFP [CX3001] R5F21335ANFP [CX3001]  
R5F21335CDFP [CX3001] R5F21335CNFP [CX3001]  
R5F21335DDFP [CX3001] R5F21335DNFP [CX3001]

R5F21335MDFP [CX3001] R5F21335MNFP [CX3001]  
R5F21335TDFP [CX3001] R5F21335TNFP [CX3001]  
R5F21336ADFP [CX3001] R5F21336ANFP [CX3001]  
R5F21336CDFP [CX3001] R5F21336CNFP [CX3001]  
R5F21336DDFP [CX3001] R5F21336DNFP [CX3001]  
R5F21336MDFP [CX3001] R5F21336MNFP [CX3001]  
R5F21336TDFP [CX3001] R5F21336TNFP [CX3001]  
R5F21346EJFP@QFP48 [CX3007] R5F21346EKFP@QFP48 [CX3007]  
R5F21346FJFP@QFP48 [CX3007] R5F21346FKFP@QFP48 [CX3007]  
R5F21346GJFP@QFP48 [CX3007] R5F21346GKFP@QFP48 [CX3007]  
R5F21346HJFP@QFP48 [CX3007] R5F21346HKFP@QFP48 [CX3007]  
R5F21346WJFP [CX3007] R5F21346WKFP [CX3007]  
R5F21347EJFP@QFP48 [CX3007] R5F21347EKFP@QFP48 [CX3007]  
R5F21347FJFP@QFP48 [CX3007] R5F21347FKFP@QFP48 [CX3007]  
R5F21347GJFP@QFP48 [CX3007] R5F21347GKFP@QFP48 [CX3007]  
R5F21347HJFP@QFP48 [CX3007] R5F21347HKFP@QFP48 [CX3007]  
R5F21347WJFP [CX3007] R5F21347WKFP [CX3007]  
R5F21348EJFP@QFP48 [CX3007] R5F21348EKFP@QFP48 [CX3007]  
R5F21348FJFP@QFP48 [CX3007] R5F21348FKFP@QFP48 [CX3007]  
R5F21348GJFP@QFP48 [CX3007] R5F21348GKFP@QFP48 [CX3007]  
R5F21348HJFP@QFP48 [CX3007] R5F21348HKFP@QFP48 [CX3007]  
R5F21348WJFP [CX3007] R5F21348WKFP [CX3007]  
R5F2134AEJFP@QFP48 [CX3007] R5F2134AEKFP@QFP48 [CX3007]  
R5F2134AFJFP@QFP48 [CX3007] R5F2134AFKFP@QFP48 [CX3007]  
R5F2134AGJFP@QFP48 [CX3007] R5F2134AGKFP@QFP48 [CX3007]  
R5F2134AHJFP@QFP48 [CX3007] R5F2134AHKFP@QFP48 [CX3007]  
R5F2134AWJFP [CX3007] R5F2134AWKFP [CX3007]  
R5F2134CEJFP@QFP48 [CX3007] R5F2134CEKFP@QFP48 [CX3007]  
R5F2134CFJFP@QFP48 [CX3007] R5F2134CFKFP@QFP48 [CX3007]  
R5F2134CGJFP@QFP48 [CX3007] R5F2134CGKFP@QFP48 [CX3007]  
R5F2134CHJFP@QFP48 [CX3007] R5F2134CHKFP@QFP48 [CX3007]  
R5F2134CWJFP [CX3007] R5F2134CWKFP [CX3007]  
R5F21354ADFP@QFP52(single wire) [CX3010]  
R5F21354ANFP@QFP52(single wire) [CX3010]  
R5F21354BDFP@QFP52(single wire) [CX3010]  
R5F21354BNFP@QFP52(single wire) [CX3010]  
R5F21354CDFP@QFP52(single wire) [CX3010]  
R5F21354CNFP@QFP52(single wire) [CX3010]  
R5F21355ADFP@QFP52(single wire) [CX3010]  
R5F21355ANFP@QFP52(single wire) [CX3010]  
R5F21355BDFP@QFP52(single wire) [CX3010]  
R5F21355BNFP@QFP52(single wire) [CX3010]  
R5F21355CDFP@QFP52(single wire) [CX3010]  
R5F21355CNFP@QFP52(single wire) [CX3010]  
R5F21356ADFP@QFP52(single wire) [CX3010]  
R5F21356ANFP@QFP52(single wire) [CX3010]  
R5F21356BDFP@QFP52(single wire) [CX3010]  
R5F21356BNFP@QFP52(single wire) [CX3010]  
R5F21356CDFP@QFP52(single wire) [CX3010]  
R5F21356CNFP@QFP52(single wire) [CX3010]  
R5F21357ADFP@QFP52(single wire) [CX3010]  
R5F21357ANFP@QFP52(single wire) [CX3010]  
R5F21357BDFP@QFP52(single wire) [CX3010]  
R5F21357BNFP@QFP52(single wire) [CX3010]  
R5F21357CDFP@QFP52(single wire) [CX3010]  
R5F21357CNFP@QFP52(single wire) [CX3010]  
R5F21358ADFP@QFP52(single wire) [CX3010]  
R5F21358ANFP@QFP52(single wire) [CX3010]  
R5F21358BDFP@QFP52(single wire) [CX3010]

R5F21358BNFP@QFP52(single wire) [CX3010]  
R5F21358CDFP@QFP52(single wire) [CX3010]  
R5F21358CNFP@QFP52(single wire) [CX3010]  
R5F2135AADFP@QFP52(single wire) [CX3010]  
R5F2135AANFP@QFP52(single wire) [CX3010]  
R5F2135ABDFP@QFP52(single wire) [CX3010]  
R5F2135ABNFP@QFP52(single wire) [CX3010]  
R5F2135ACDFP@QFP52(single wire) [CX3010]  
R5F2135ACNFP@QFP52(single wire) [CX3010]  
R5F2135CADFP@QFP52(single wire) [CX3010]  
R5F2135CANFP@QFP52(single wire) [CX3010]  
R5F2135CBDFP@QFP52(single wire) [CX3010]  
R5F2135CBNFP@QFP52(single wire) [CX3010]  
R5F2135CCDFP@QFP52(single wire) [CX3010]  
R5F2135CCNFP@QFP52(single wire) [CX3010]  
R5F21364ADFA [CX3013] R5F21364ADFP [CX3011]  
R5F21364ANFA [CX3013] R5F21364ANFP [CX3011]  
R5F21364CDFA [CX3013] R5F21364CDFP [CX3011]  
R5F21364CNFA [CX3013] R5F21364CNFP [CX3011]  
R5F21365ADFA [CX3013] R5F21365ADFP [CX3011]  
R5F21365ANFA [CX3013] R5F21365ANFP [CX3011]  
R5F21365CDFA [CX3013] R5F21365CDFP [CX3011]  
R5F21365CNFA [CX3013] R5F21365CNFP [CX3011]  
R5F21366ADFA [CX3013] R5F21366ADFP [CX3011]  
R5F21366ANFA [CX3013] R5F21366ANFP [CX3011]  
R5F21366CDFA [CX3013] R5F21366CDFP [CX3011]  
R5F21366CNFA [CX3013] R5F21366CNFP [CX3011]  
R5F21367ADFA [CX3013] R5F21367ADFP [CX3011]  
R5F21367ANFA [CX3013] R5F21367ANFP [CX3011]  
R5F21367CDFA [CX3013] R5F21367CDFP [CX3011]  
R5F21367CNFA [CX3013] R5F21367CNFP [CX3011]  
R5F21368ADFA [CX3013] R5F21368ADFP [CX3011]  
R5F21368ANFA [CX3013] R5F21368ANFP [CX3011]  
R5F21368CDFA [CX3013] R5F21368CDFP [CX3011]  
R5F21368CNFA [CX3013] R5F21368CNFP [CX3011]  
R5F2136AADFA [CX3013] R5F2136AADFP [CX3011]  
R5F2136AANFA [CX3013] R5F2136AANFP [CX3011]  
R5F2136ACDFA [CX3013] R5F2136ACDFP [CX3011]  
R5F2136ACNFA [CX3013] R5F2136ACNFP [CX3011]  
R5F2136CADFA [CX3013] R5F2136CADFP [CX3011]  
R5F2136CANFA [CX3013] R5F2136CANFP [CX3011]  
R5F2136CCDFA [CX3013] R5F2136CCDFP [CX3011]  
R5F2136CCNFA [CX3013] R5F2136CCNFP [CX3011]  
R5F213G1DDSP [CX1026] R5F213G1DNSP [CX1026]  
R5F213G2DDSP [CX1026] R5F213G2DNSP [CX1026]  
R5F213G4DDSP [CX1026] R5F213G4DNSP [CX1026]  
R5F213G5DDSP [CX1026] R5F213G5DNSP [CX1026]  
R5F213G6DDSP [CX1026] R5F213G6DNSP [CX1026]  
R5F2L357ADFP@QFP52 [CX3010]  
R5F2L357ADFP@QFP52(single wire) [CX3010]  
R5F2L357ANFP@QFP52 [CX3010]  
R5F2L357ANFP@QFP52(single wire) [CX3010]  
R5F2L357BDFP@QFP52 [CX3010]  
R5F2L357BDFP@QFP52(single wire) [CX3010]  
R5F2L357BNFP@QFP52 [CX3010]  
R5F2L357BNFP@QFP52(single wire) [CX3010]  
R5F2L357CDFP@QFP52 [CX3010]  
R5F2L357CDFP@QFP52(single wire) [CX3010]  
R5F2L357CNFP@QFP52 [CX3010]

R5F2L357CNFP@QFP52(single wire) [CX3010]  
R5F2L358ADFP@QFP52 [CX3010]  
R5F2L358ADFP@QFP52(single wire) [CX3010]  
R5F2L358ANFP@QFP52 [CX3010]  
R5F2L358ANFP@QFP52(single wire) [CX3010]  
R5F2L358BDFP@QFP52 [CX3010]  
R5F2L358BDFP@QFP52(single wire) [CX3010]  
R5F2L358BNFP@QFP52 [CX3010]  
R5F2L358BNFP@QFP52(single wire) [CX3010]  
R5F2L358CDFP@QFP52 [CX3010]  
R5F2L358CDFP@QFP52(single wire) [CX3010]  
R5F2L358CNFP@QFP52 [CX3010]  
R5F2L358CNFP@QFP52(single wire) [CX3010]  
R5F2L35AADFP@QFP52 [CX3010]  
R5F2L35AADFP@QFP52(single wire) [CX3010]  
R5F2L35AANFP@QFP52 [CX3010]  
R5F2L35AANFP@QFP52(single wire) [CX3010]  
R5F2L35ABDFP@QFP52 [CX3010]  
R5F2L35ABDFP@QFP52(single wire) [CX3010]  
R5F2L35ABNFP@QFP52 [CX3010]  
R5F2L35ABNFP@QFP52(single wire) [CX3010]  
R5F2L35ACDFP@QFP52 [CX3010]  
R5F2L35ACDFP@QFP52(single wire) [CX3010]  
R5F2L35ACNFP@QFP52 [CX3010]  
R5F2L35ACNFP@QFP52(single wire) [CX3010]  
R5F2L35CADFP@QFP52 [CX3010]  
R5F2L35CADFP@QFP52(single wire) [CX3010]  
R5F2L35CANFP@QFP52 [CX3010]  
R5F2L35CANFP@QFP52(single wire) [CX3010]  
R5F2L35CBDFP@QFP52 [CX3010]  
R5F2L35CBDFP@QFP52(single wire) [CX3010]  
R5F2L35CBNFP@QFP52 [CX3010]  
R5F2L35CBNFP@QFP52(single wire) [CX3010]  
R5F2L35CCDFP@QFP52 [CX3010]  
R5F2L35CCDFP@QFP52(single wire) [CX3010]  
R5F2L35CCNFP@QFP52 [CX3010]  
R5F2L35CCNFP@QFP52(single wire) [CX3010]  
R5F2L367ADFA@QFP64 [CX3013]  
R5F2L367ADFA@QFP64(single wire) [CX3013]  
R5F2L367ADFP@QFP64 [CX3011]  
R5F2L367ADFP@QFP64(single wire) [CX3011]  
R5F2L367ANFA@QFP64 [CX3013]  
R5F2L367ANFA@QFP64(single wire) [CX3013]  
R5F2L367ANFP@QFP64 [CX3011]  
R5F2L367ANFP@QFP64(single wire) [CX3011]  
R5F2L367BDFA@QFP64 [CX3013]  
R5F2L367BDFA@QFP64(single wire) [CX3013]  
R5F2L367BDFP@QFP64 [CX3011]  
R5F2L367BDFP@QFP64(single wire) [CX3011]  
R5F2L367BNFA@QFP64 [CX3013]  
R5F2L367BNFA@QFP64(single wire) [CX3013]  
R5F2L367BNFP@QFP64 [CX3011]  
R5F2L367BNFP@QFP64(single wire) [CX3011]  
R5F2L367CDFA@QFP64 [CX3013]  
R5F2L367CDFA@QFP64(single wire) [CX3013]  
R5F2L367CDFP@QFP64 [CX3011]  
R5F2L367CDFP@QFP64(single wire) [CX3011]  
R5F2L367CNFA@QFP64 [CX3013]  
R5F2L367CNFA@QFP64(single wire) [CX3013]

R5F2L367CNFP@QFP64 [CX3011]  
R5F2L367CNFP@QFP64(single wire) [CX3011]  
R5F2L368ADFA@QFP64 [CX3013]  
R5F2L368ADFA@QFP64(single wire) [CX3013]  
R5F2L368ADFP@QFP64 [CX3011]  
R5F2L368ADFP@QFP64(single wire) [CX3011]  
R5F2L368ANFA@QFP64 [CX3013]  
R5F2L368ANFA@QFP64(single wire) [CX3013]  
R5F2L368ANFP@QFP64 [CX3011]  
R5F2L368ANFP@QFP64(single wire) [CX3011]  
R5F2L368BDFA@QFP64 [CX3013]  
R5F2L368BDFA@QFP64(single wire) [CX3013]  
R5F2L368BDFP@QFP64 [CX3011]  
R5F2L368BDFP@QFP64(single wire) [CX3011]  
R5F2L368BNFA@QFP64 [CX3013]  
R5F2L368BNFA@QFP64(single wire) [CX3013]  
R5F2L368BNFP@QFP64 [CX3011]  
R5F2L368BNFP@QFP64(single wire) [CX3011]  
R5F2L368CDFA@QFP64 [CX3013]  
R5F2L368CDFA@QFP64(single wire) [CX3013]  
R5F2L368CDFP@QFP64 [CX3011]  
R5F2L368CDFP@QFP64(single wire) [CX3011]  
R5F2L368CNFA@QFP64 [CX3013]  
R5F2L368CNFA@QFP64(single wire) [CX3013]  
R5F2L368CNFP@QFP64 [CX3011]  
R5F2L368CNFP@QFP64(single wire) [CX3011]  
R5F2L36AADFA@QFP64 [CX3013]  
R5F2L36AADFA@QFP64(single wire) [CX3013]  
R5F2L36AADFP@QFP64 [CX3011]  
R5F2L36AADFP@QFP64(single wire) [CX3011]  
R5F2L36AANFA@QFP64 [CX3013]  
R5F2L36AANFA@QFP64(single wire) [CX3013]  
R5F2L36AANFP@QFP64 [CX3011]  
R5F2L36AANFP@QFP64(single wire) [CX3011]  
R5F2L36ABDFA@QFP64 [CX3013]  
R5F2L36ABDFA@QFP64(single wire) [CX3013]  
R5F2L36ABDFP@QFP64 [CX3011]  
R5F2L36ABDFP@QFP64(single wire) [CX3011]  
R5F2L36ABNFA@QFP64 [CX3013]  
R5F2L36ABNFA@QFP64(single wire) [CX3013]  
R5F2L36ABNFP@QFP64 [CX3011]  
R5F2L36ABNFP@QFP64(single wire) [CX3011]  
R5F2L36ACDFA@QFP64 [CX3013]  
R5F2L36ACDFA@QFP64(single wire) [CX3013]  
R5F2L36ACDFP@QFP64 [CX3011]  
R5F2L36ACDFP@QFP64(single wire) [CX3011]  
R5F2L36ACNFA@QFP64 [CX3013]  
R5F2L36ACNFA@QFP64(single wire) [CX3013]  
R5F2L36ACNFP@QFP64 [CX3011]  
R5F2L36ACNFP@QFP64(single wire) [CX3011]  
R5F2L36CADFA@QFP64 [CX3013]  
R5F2L36CADFA@QFP64(single wire) [CX3013]  
R5F2L36CADFP@QFP64 [CX3011]  
R5F2L36CADFP@QFP64(single wire) [CX3011]  
R5F2L36CANFA@QFP64 [CX3013]  
R5F2L36CANFA@QFP64(single wire) [CX3013]  
R5F2L36CANFP@QFP64 [CX3011]  
R5F2L36CANFP@QFP64(single wire) [CX3011]  
R5F2L36CBDFA@QFP64 [CX3013]

R5F2L36CBDF@QFP64(single wire) [CX3013]  
R5F2L36CBDFP@QFP64 [CX3011]  
R5F2L36CBDFP@QFP64(single wire) [CX3011]  
R5F2L36CBNFA@QFP64 [CX3013]  
R5F2L36CBNFA@QFP64(single wire) [CX3013]  
R5F2L36CBNFP@QFP64 [CX3011]  
R5F2L36CBNFP@QFP64(single wire) [CX3011]  
R5F2L36CCDFA@QFP64 [CX3013]  
R5F2L36CCDFA@QFP64(single wire) [CX3013]  
R5F2L36CCDFP@QFP64 [CX3011]  
R5F2L36CCDFP@QFP64(single wire) [CX3011]  
R5F2L36CCNFA@QFP64 [CX3013]  
R5F2L36CCNFA@QFP64(single wire) [CX3013]  
R5F2L36CCNFP@QFP64 [CX3011]  
R5F2L36CCNFP@QFP64(single wire) [CX3011]  
R5F2L387ADFA@QFP80 [CX3018]  
R5F2L387ADFA@QFP80(single wire) [CX3018]  
R5F2L387ADFP@QFP80 [CX3016]  
R5F2L387ADFP@QFP80(single wire) [CX3016]  
R5F2L387ANFA@QFP80 [CX3018]  
R5F2L387ANFA@QFP80(single wire) [CX3018]  
R5F2L387ANFP@QFP80 [CX3016]  
R5F2L387ANFP@QFP80(single wire) [CX3016]  
R5F2L387BDFA@QFP80 [CX3018]  
R5F2L387BDFA@QFP80(single wire) [CX3018]  
R5F2L387BDFP@QFP80 [CX3016]  
R5F2L387BDFP@QFP80(single wire) [CX3016]  
R5F2L387BNFA@QFP80 [CX3018]  
R5F2L387BNFA@QFP80(single wire) [CX3018]  
R5F2L387BNFP@QFP80 [CX3016]  
R5F2L387BNFP@QFP80(single wire) [CX3016]  
R5F2L387CDFA@QFP80 [CX3018]  
R5F2L387CDFA@QFP80(single wire) [CX3018]  
R5F2L387CDFP@QFP80 [CX3016]  
R5F2L387CDFP@QFP80(single wire) [CX3016]  
R5F2L387CNFA@QFP80 [CX3018]  
R5F2L387CNFA@QFP80(single wire) [CX3018]  
R5F2L387CNFP@QFP80 [CX3016]  
R5F2L387CNFP@QFP80(single wire) [CX3016]  
R5F2L388ADFA@QFP80 [CX3018]  
R5F2L388ADFA@QFP80(single wire) [CX3018]  
R5F2L388ADFP@QFP80 [CX3016]  
R5F2L388ADFP@QFP80(single wire) [CX3016]  
R5F2L388ANFA@QFP80 [CX3018]  
R5F2L388ANFA@QFP80(single wire) [CX3018]  
R5F2L388ANFP@QFP80 [CX3016]  
R5F2L388ANFP@QFP80(single wire) [CX3016]  
R5F2L388BDFA@QFP80 [CX3018]  
R5F2L388BDFA@QFP80(single wire) [CX3018]  
R5F2L388BDFP@QFP80 [CX3016]  
R5F2L388BDFP@QFP80(single wire) [CX3016]  
R5F2L388BNFA@QFP80 [CX3018]  
R5F2L388BNFA@QFP80(single wire) [CX3018]  
R5F2L388BNFP@QFP80 [CX3016]  
R5F2L388BNFP@QFP80(single wire) [CX3016]  
R5F2L388CDFA@QFP80 [CX3018]  
R5F2L388CDFA@QFP80(single wire) [CX3018]  
R5F2L388CDFP@QFP80 [CX3016]  
R5F2L388CDFP@QFP80(single wire) [CX3016]

R5F2L388CNFA@QFP80 [CX3018]  
R5F2L388CNFA@QFP80(single wire) [CX3018]  
R5F2L388CNFP@QFP80 [CX3016]  
R5F2L388CNFP@QFP80(single wire) [CX3016]  
R5F2L38AADFA@QFP80 [CX3018]  
R5F2L38AADFA@QFP80(single wire) [CX3018]  
R5F2L38AADFP@QFP80 [CX3016]  
R5F2L38AADFP@QFP80(single wire) [CX3016]  
R5F2L38AANFA@QFP80 [CX3018]  
R5F2L38AANFA@QFP80(single wire) [CX3018]  
R5F2L38AANFP@QFP80 [CX3016]  
R5F2L38AANFP@QFP80(single wire) [CX3016]  
R5F2L38ABDFA@QFP80 [CX3018]  
R5F2L38ABDFA@QFP80(single wire) [CX3018]  
R5F2L38ABDFP@QFP80 [CX3016]  
R5F2L38ABDFP@QFP80(single wire) [CX3016]  
R5F2L38ABNFA@QFP80 [CX3018]  
R5F2L38ABNFA@QFP80(single wire) [CX3018]  
R5F2L38ABNFP@QFP80 [CX3016]  
R5F2L38ABNFP@QFP80(single wire) [CX3016]  
R5F2L38ACDFA@QFP80 [CX3018]  
R5F2L38ACDFA@QFP80(single wire) [CX3018]  
R5F2L38ACDFP@QFP80 [CX3016]  
R5F2L38ACDFP@QFP80(single wire) [CX3016]  
R5F2L38ACNFA@QFP80 [CX3018]  
R5F2L38ACNFA@QFP80(single wire) [CX3018]  
R5F2L38ACNFP@QFP80 [CX3016]  
R5F2L38ACNFP@QFP80(single wire) [CX3016]  
R5F2L38CADFA@QFP80 [CX3018]  
R5F2L38CADFA@QFP80(single wire) [CX3018]  
R5F2L38CADFP@QFP80 [CX3016]  
R5F2L38CADFP@QFP80(single wire) [CX3016]  
R5F2L38CANFA@QFP80 [CX3018]  
R5F2L38CANFA@QFP80(single wire) [CX3018]  
R5F2L38CANFP@QFP80 [CX3016]  
R5F2L38CANFP@QFP80(single wire) [CX3016]  
R5F2L38CBDFA@QFP80 [CX3018]  
R5F2L38CBDFA@QFP80(single wire) [CX3018]  
R5F2L38CBDFP@QFP80 [CX3016]  
R5F2L38CBDFP@QFP80(single wire) [CX3016]  
R5F2L38CBNFA@QFP80 [CX3018]  
R5F2L38CBNFA@QFP80(single wire) [CX3018]  
R5F2L38CBNFP@QFP80 [CX3016]  
R5F2L38CBNFP@QFP80(single wire) [CX3016]  
R5F2L38CCDFA@QFP80 [CX3018]  
R5F2L38CCDFA@QFP80(single wire) [CX3018]  
R5F2L38CCDFP@QFP80 [CX3016]  
R5F2L38CCDFP@QFP80(single wire) [CX3016]  
R5F2L38CCNFA@QFP80 [CX3018]  
R5F2L38CCNFA@QFP80(single wire) [CX3018]  
R5F2L38CCNFP@QFP80 [CX3016]  
R5F2L38CCNFP@QFP80(single wire) [CX3016]  
R5F2L3A7ADFA@PQFP100 [CX3023]  
R5F2L3A7ADFA@PQFP100(single) [CX3023]  
R5F2L3A7ADFP@PQFP100 [CX3021]  
R5F2L3A7ADFP@PQFP100(single) [CX3021]  
R5F2L3A7ANFA@PQFP100 [CX3023]  
R5F2L3A7ANFA@PQFP100(single) [CX3023]  
R5F2L3A7ANFP@PQFP100 [CX3021]



R5F2L3A7ANFP@PQFP100(single) [CX3021]  
R5F2L3A7BDFA@PQFP100 [CX3023]  
R5F2L3A7BDFA@PQFP100(single) [CX3023]  
R5F2L3A7BDFA@PQFP100 [CX3021]  
R5F2L3A7BDFA@PQFP100(single) [CX3021]  
R5F2L3A7BNFA@PQFP100 [CX3023]  
R5F2L3A7BNFA@PQFP100(single) [CX3023]  
R5F2L3A7BNFA@PQFP100 [CX3021]  
R5F2L3A7BNFA@PQFP100(single) [CX3021]  
R5F2L3A7CDFA@PQFP100 [CX3023]  
R5F2L3A7CDFA@PQFP100(single) [CX3023]  
R5F2L3A7CDFP@PQFP100 [CX3021]  
R5F2L3A7CDFP@PQFP100(single) [CX3021]  
R5F2L3A7CNFA@PQFP100 [CX3023]  
R5F2L3A7CNFA@PQFP100(single) [CX3023]  
R5F2L3A7CNFA@PQFP100 [CX3021]  
R5F2L3A7CNFA@PQFP100(single) [CX3021]  
R5F2L3A8ADFA@PQFP100 [CX3023]  
R5F2L3A8ADFA@PQFP100(single) [CX3023]  
R5F2L3A8ADFA@PQFP100 [CX3021]  
R5F2L3A8ADFA@PQFP100(single) [CX3021]  
R5F2L3A8ANFA@PQFP100 [CX3023]  
R5F2L3A8ANFA@PQFP100(single) [CX3023]  
R5F2L3A8ANFP@PQFP100 [CX3021]  
R5F2L3A8ANFP@PQFP100(single) [CX3021]  
R5F2L3A8BDFA@PQFP100 [CX3023]  
R5F2L3A8BDFA@PQFP100(single) [CX3023]  
R5F2L3A8BDFA@PQFP100 [CX3021]  
R5F2L3A8BDFA@PQFP100(single) [CX3021]  
R5F2L3A8BNFA@PQFP100 [CX3023]  
R5F2L3A8BNFA@PQFP100(single) [CX3023]  
R5F2L3A8BNFA@PQFP100 [CX3021]  
R5F2L3A8BNFA@PQFP100(single) [CX3021]  
R5F2L3A8CDFA@PQFP100 [CX3023]  
R5F2L3A8CDFA@PQFP100(single) [CX3023]  
R5F2L3A8CDFP@PQFP100 [CX3021]  
R5F2L3A8CDFP@PQFP100(single) [CX3021]  
R5F2L3A8CNFA@PQFP100 [CX3023]  
R5F2L3A8CNFA@PQFP100(single) [CX3023]  
R5F2L3A8CNFA@PQFP100 [CX3021]  
R5F2L3A8CNFA@PQFP100(single) [CX3021]  
R5F2L3AAADFA@PQFP100 [CX3023]  
R5F2L3AAADFA@PQFP100(single) [CX3023]  
R5F2L3AAADFA@PQFP100 [CX3021]  
R5F2L3AAADFA@PQFP100(single) [CX3021]  
R5F2L3AAANFA@PQFP100 [CX3023]  
R5F2L3AAANFA@PQFP100(single) [CX3023]  
R5F2L3AAANFA@PQFP100 [CX3021]  
R5F2L3AAANFA@PQFP100(single) [CX3021]  
R5F2L3AABDFA@PQFP100 [CX3023]  
R5F2L3AABDFA@PQFP100(single) [CX3023]  
R5F2L3AABDFA@PQFP100 [CX3021]  
R5F2L3AABDFA@PQFP100(single) [CX3021]  
R5F2L3AABNFA@PQFP100 [CX3023]  
R5F2L3AABNFA@PQFP100(single) [CX3023]  
R5F2L3AABNFA@PQFP100 [CX3021]  
R5F2L3AABNFA@PQFP100(single) [CX3021]  
R5F2L3AACDFA@PQFP100 [CX3023]  
R5F2L3AACDFA@PQFP100(single) [CX3023]

R5F2L3AACDFP@PQFP100 [CX3021]  
R5F2L3AACDFP@PQFP100(single) [CX3021]  
R5F2L3AACNFA@PQFP100 [CX3023]  
R5F2L3AACNFA@PQFP100(single) [CX3023]  
R5F2L3AACNFP@PQFP100 [CX3021]  
R5F2L3AACNFP@PQFP100(single) [CX3021]  
R5F2L3ACADFA@PQFP100 [CX3023]  
R5F2L3ACADFA@PQFP100(single) [CX3023]  
R5F2L3ACADFP@PQFP100 [CX3021]  
R5F2L3ACADFP@PQFP100(single) [CX3021]  
R5F2L3ACANFA@PQFP100 [CX3023]  
R5F2L3ACANFA@PQFP100(single) [CX3023]  
R5F2L3ACANFP@PQFP100 [CX3021]  
R5F2L3ACANFP@PQFP100(single) [CX3021]  
R5F2L3ACBDFA@PQFP100 [CX3023]  
R5F2L3ACBDFA@PQFP100(single) [CX3023]  
R5F2L3ACBDFP@PQFP100 [CX3021]  
R5F2L3ACBDFP@PQFP100(single) [CX3021]  
R5F2L3ACBNFA@PQFP100 [CX3023]  
R5F2L3ACBNFA@PQFP100(single) [CX3023]  
R5F2L3ACBNFP@PQFP100 [CX3021]  
R5F2L3ACBNFP@PQFP100(single) [CX3021]  
R5F2L3ACCDFA@PQFP100 [CX3023]  
R5F2L3ACCDFA@PQFP100(single) [CX3023]  
R5F2L3ACCDFP@PQFP100 [CX3021]  
R5F2L3ACCDFP@PQFP100(single) [CX3021]  
R5F2L3ACCNFA@PQFP100 [CX3023]  
R5F2L3ACCNFA@PQFP100(single) [CX3023]  
R5F2L3ACCNFP@PQFP100 [CX3021]  
R5F2L3ACCNFP@PQFP100(single) [CX3021]  
R5F2M110ADDD(single) [CX0001]  
R5F2M110ADSP@TSSOP14(single) [CX1000]  
R5F2M110ANDD(single) [CX0001]  
R5F2M110ANSP@TSSOP14(single) [CX1000]  
R5F2M111ADDD(single) [CX0001]  
R5F2M111ADSP@TSSOP14(single) [CX1000]  
R5F2M111ANDD(single) [CX0001]  
R5F2M111ANSP@TSSOP14(single) [CX1000]  
R5F2M112ADDD(single) [CX0001]  
R5F2M112ADSP@TSSOP14(single) [CX1000]  
R5F2M112ANDD(single) [CX0001]  
R5F2M112ANSP@TSSOP14(single) [CX1000]  
R5F2M120ADDD(single) [CX0001]  
R5F2M120ADSP@TSSOP20(single) [CX1000]  
R5F2M120ANDD(single) [CX0001]  
R5F2M120ANSP@TSSOP20(single) [CX1000]  
R5F2M121ADDD(single) [CX0001]  
R5F2M121ADSP@TSSOP20(single) [CX1000]  
R5F2M121ANDD(single) [CX0001]  
R5F2M121ANSP@TSSOP20(single) [CX1000]  
R5F2M122ADDD(single) [CX0001]  
R5F2M122ADSP@TSSOP20(single) [CX1000]  
R5F2M122ANDD(single) [CX0001]  
R5F2M122ANSP@TSSOP20(single) [CX1000]  
R5F35623JFE [CX3016] R5F35623KFE [CX3016]  
R5F35626JFE [CX3016] R5F35626KFE [CX3016]  
R5F3562EJFE [CX3016] R5F3562EKFE [CX3016]  
R5F35630JFF [CX3011] R5F35630KFF [CX3011]  
R5F35633JFF [CX3011] R5F35633KFF [CX3011]

R5F35636JFF [CX3011]	R5F35636KFF [CX3011]
R5F3563EJFF [CX3011]	R5F3563EKFF [CX3011]
R5F35L23JFE [CX3016]	R5F35L23KFE [CX3016]
R5F35L26JFE [CX3016]	R5F35L26KFE [CX3016]
R5F35L2EJFE [CX3016]	R5F35L2EKFE [CX3016]
R5F35L30JFF [CX3011]	R5F35L30KFF [CX3011]
R5F35L33JFF [CX3011]	R5F35L33KFF [CX3011]
R5F35L36JFF [CX3011]	R5F35L36KFF [CX3011]
R5F35L3EJFF [CX3011]	R5F35L3EKFF [CX3011]
R5F363A6DFA@PQFP100 [CX3022]	R5F363A6DFB@QFP100 [CX3021]
R5F363A6NFA@PQFP100 [CX3022]	R5F363A6NFB@QFP100 [CX3021]
R5F363AEDFA@PQFP100 [CX3022]	R5F363AEDFB@QFP100 [CX3021]
R5F363AENFA@PQFP100 [CX3022]	R5F363AENFB@QFP100 [CX3021]
R5F363AKDFA@PQFP100 [CX3022]	R5F363AKDFB@QFP100 [CX3021]
R5F363AKNFA@PQFP100 [CX3022]	R5F363AKNFB@QFP100 [CX3021]
R5F363AMDFA@PQFP100 [CX3022]	R5F363AMDFB@QFP100 [CX3021]
R5F363AMNFA@PQFP100 [CX3022]	R5F363AMNFB@QFP100 [CX3021]
R5F36406DFA@PQFP100 [CX3022]	R5F36406DFB@QFP100 [CX3021]
R5F36406NFA@PQFP100 [CX3022]	R5F36406NFB@QFP100 [CX3021]
R5F3640DDFA@PQFP100 [CX3022]	R5F3640DDFB@QFP100 [CX3021]
R5F3640DNFA@PQFP100 [CX3022]	R5F3640DNFB@QFP100 [CX3021]
R5F3640MDFA@PQFP100 [CX3022]	R5F3640MDFB@QFP100 [CX3021]
R5F3640MNFA@PQFP100 [CX3022]	R5F3640MNFB@QFP100 [CX3021]
R5F364A6DFA@PQFP100 [CX3022]	R5F364A6DFB@QFP100 [CX3021]
R5F364A6NFA@PQFP100 [CX3022]	R5F364A6NFB@QFP100 [CX3021]
R5F364AEDFA@PQFP100 [CX3022]	R5F364AEDFB@QFP100 [CX3021]
R5F364AENFA@PQFP100 [CX3022]	R5F364AENFB@QFP100 [CX3021]
R5F364AMDFA@PQFP100 [CX3022]	R5F364AMDFB@QFP100 [CX3021]
R5F364AMNFA@PQFP100 [CX3022]	R5F364AMNFB@QFP100 [CX3021]
R5F36506DFA@PQFP100 [CX3022]	R5F36506DFB@QFP100 [CX3021]
R5F36506NFA@PQFP100 [CX3022]	R5F36506NFB@QFP100 [CX3021]
R5F3650EDFA@PQFP100 [CX3022]	R5F3650EDFB@QFP100 [CX3021]
R5F3650ENFA@PQFP100 [CX3022]	R5F3650ENFB@QFP100 [CX3021]
R5F3650KDFA@PQFP100 [CX3022]	R5F3650KDFB@QFP100 [CX3021]
R5F3650KNFA@PQFP100 [CX3022]	R5F3650KNFB@QFP100 [CX3021]
R5F3650MDFA@PQFP100 [CX3022]	R5F3650MDFB@QFP100 [CX3021]
R5F3650MNFA@PQFP100 [CX3022]	R5F3650MNFB@QFP100 [CX3021]
R5F3650NDFA@PQFP100 [CX3022]	R5F3650NDFB@QFP100 [CX3021]
R5F3650NNFA@PQFP100 [CX3022]	R5F3650NNFB@QFP100 [CX3021]
R5F3650RDFA@PQFP100 [CX3022]	R5F3650RDFB@QFP100 [CX3021]
R5F3650RNFA@PQFP100 [CX3022]	R5F3650RNFB@QFP100 [CX3021]
R5F3650TDFA@PQFP100 [CX3022]	R5F3650TDFB@QFP100 [CX3021]
R5F3650TNFA@PQFP100 [CX3022]	R5F3650TNFB@QFP100 [CX3021]
R5G0C314D@SDIP32 [CX0032]	R5G0C328FA@QFP32 [CX3001]
R5R0C0B4SP@TSSOP24(single wire) [CX1012]	

## MOSEL-VITELIC

### E (E) PROM / FRAM / NVRAM

V29C31004B [CX0001]	V29C31004B@PLCC32 [CX2032]
V29C31004B@TSOP32 [CX1002]	V29C31004T [CX0001]
V29C31004T@PLCC32 [CX2032]	V29C31004T@TSOP32 [CX1002]
V29C51000B [CX0001]	V29C51000B@PLCC32 [CX2032]
V29C51000B@TSOP32 [CX1002]	V29C51000T [CX0001]
V29C51000T@PLCC32 [CX2032]	V29C51000T@TSOP32 [CX1002]
V29C51001B [CX0001]	V29C51001B@PLCC32 [CX2032]
V29C51001B@TSOP32 [CX1002]	V29C51001T [CX0001]

V29C51001T@PLCC32 [CX2032]  
V29C51002B [CX0001]  
V29C51002B@TSOP32 [CX1002]  
V29C51002T@PLCC32 [CX2032]  
V29C51004B [CX0001]  
V29C51004B@TSOP32 [CX1002]  
V29C51004T@PLCC32 [CX2032]  
V29LC51000 [CX0001]  
V29LC51000@TSOP32 [CX1002]  
V29LC51001@PLCC32 [CX2032]  
V29LC51002 [CX0001]  
V29LC51002@TSOP32 [CX1002]

V29C51001T@TSOP32 [CX1002]  
V29C51002B@PLCC32 [CX2032]  
V29C51002T [CX0001]  
V29C51002T@TSOP32 [CX1002]  
V29C51004B@PLCC32 [CX2032]  
V29C51004T [CX0001]  
V29C51004T@TSOP32 [CX1002]  
V29LC51000@PLCC32 [CX2032]  
V29LC51001 [CX0001]  
V29LC51001@TSOP32 [CX1002]  
V29LC51002@PLCC32 [CX2032]

## MICROCONTROLLER

MSU1958 [CX0001]  
MSU1958@TQFP44 [CX3002]  
MSU2952@PLCC44 [CX2044]  
MSU2958 [CX0001]  
MSU2958@TQFP44 [CX3002]  
MSU2964@PLCC44 [CX2044]

MSU1958@PLCC44 [CX2044]  
MSU2952 [CX0001]  
MSU2952@TQFP44 [CX3002]  
MSU2958@PLCC44 [CX2044]  
MSU2964 [CX0001]  
MSU2964@TQFP44 [CX3002]

## MOSMIC

### MICROCONTROLLER

MOS33001 [CX0001]  
MOS33001@TQFP44 [CX3005]  
MOS33002@PLCC44 [CX2044]  
MOS33004 [CX0001]  
MOS33004@TQFP44 [CX3005]  
MOS33008@PLCC44 [CX2044]  
MOS33016 [CX0001]  
MOS33016@TQFP44 [CX3005]  
MOS33032@PLCC44 [CX2044]  
MOS33064 [CX0001]  
MOS33064@TQFP44 [CX3005]  
MOS33128@PLCC44 [CX2044]  
MOS33256 [CX0001]  
MOS33256@TQFP44 [CX3005]

MOS33001@PLCC44 [CX2044]  
MOS33002 [CX0001]  
MOS33002@TQFP44 [CX3005]  
MOS33004@PLCC44 [CX2044]  
MOS33008 [CX0001]  
MOS33008@TQFP44 [CX3005]  
MOS33016@PLCC44 [CX2044]  
MOS33032 [CX0001]  
MOS33032@TQFP44 [CX3005]  
MOS33064@PLCC44 [CX2044]  
MOS33128 [CX0001]  
MOS33128@TQFP44 [CX3005]  
MOS33256@PLCC44 [CX2044]

## MOSTEK

### E (E) PROM/FRAM/NVRAM

ET2716 [CX0001]  
ETC2732 [CX0001]  
MK2764 [CX0001]  
MK48C12 [CX0001]  
MK48T08 [CX0001]  
MK48T12B [CX0001]  
MK48Z02 [CX0001]  
MK48Z12 [CX0001]  
MK48Z18 [CX0001]

ETC2716 [CX0001]  
MK2716 [CX0001]  
MK48C02 [CX0001]  
MK48T02 [CX0001]  
MK48T12 [CX0001]  
MK48T18 [CX0001]  
MK48Z08 [CX0001]  
MK48Z12B [CX0001]

# MOTOROLA

## E (E) PROM/FRAM/NVRAM

MC68764 [CX0001]  
MCM2716 [CX0001]

MC68766 [CX0001]

## DRAM & SRAM

MCM60256A [CX0001]  
MCM60256AC [CX0001]  
MCM60256AV [CX0001]  
MCM60L256A [CX0001]  
MCM60L256AC [CX0001]  
MCM60L256AV [CX0001]  
MCM6206 [CX0001]  
MCM6206C [CX0001]  
MCM6264 [CX0001]  
MCM6264C [CX0001]  
MCM6706 [CX0001]  
MCM6706A [CX0001]

MCM60256A@SOIC28 [CX1035]  
MCM60256AC@SOIC28 [CX1035]  
MCM60256AV@SOIC28 [CX1035]  
MCM60L256A@SOIC28 [CX1035]  
MCM60L256AC@SOIC28 [CX1035]  
MCM60L256AV@SOIC28 [CX1035]  
MCM6206@SOIC28 [CX1035]  
MCM6206C@SOIC28 [CX1035]  
MCM6264@SOIC28 [CX1035]  
MCM6264C@SOIC28 [CX1035]  
MCM6706@SOIC28 [CX1035]  
MCM6706A@SOJ28 [CX1035]

## MICROCONTROLLER

DSP56F801(FA60)@TQFP48 [CX3007]  
DSP56F801(FA80)@TQFP48 [CX3007]  
DSP56F802(TA60)@TQFP32 [CX3001]  
DSP56F802(TA80)@TQFP32 [CX3001]  
MC56F8002VWL@SOIC28 [CX1033]  
MC56F8006VLF@QFP48 [CX3007]  
MC56F8011VFAE@QFP32 [CX3001]  
MC56F8014VFAE@QFP32 [CX3001]  
MC56F8023VFAE@QFP32 [CX3001]  
MC56F8027VLD@QFP64 [CX3011]  
MC56F8035VLD@QFP44 [CX3003]  
MC56F8036VFAE@QFP48 [CX3007]  
MC56F8122MFA@QFP48 [CX3007]  
MC56F8122VFA@QFP48 [CX3007]  
MC56F8123MFB@QFP64 [CX3011]  
MC56F8123VFB@QFP64 [CX3011]  
MC56F8246MLF@QFP48 [CX3007]  
MC56F8247MLH@QFP64 [CX3011]  
MC56F8256MLF@QFP48 [CX3007]  
MC56F8257MLH@QFP64 [CX3011]  
MC56F8322MFA@QFP48 [CX3007]  
MC56F8322VFA@QFP48 [CX3007]  
MC56F8323MFB@QFP64 [CX3011]  
MC56F8323VFB@QFP64 [CX3011]  
MC68HC11E1@PLCC52 [CX2052]  
MC68HC11E1CFU2 [CX3044]  
MC68HC11E1MFU2 [CX3044]  
MC68HC11E20@PLCC52 [CX2052]  
MC68HC11E20CFU2 [CX3044]  
MC68HC11E20MFU2 [CX3044]  
MC68HC11E9@PLCC52 [CX2052]  
MC68HC11E9CFU2 [CX3044]  
MC68HC11E9MFU2 [CX3044]  
MC68HC11EA9CFN2 [CX2052]

DSP56F801(FA60E)@TQFP48 [CX3007]  
DSP56F801(FA80E)@TQFP48 [CX3007]  
DSP56F802(TA60E)@TQFP32 [CX3001]  
DSP56F802(TA80E)@TQFP32 [CX3001]  
MC56F8006VLC@QFP32 [CX3001]  
MC56F8006VWL@SOIC28 [CX1033]  
MC56F8013VFAE@QFP32 [CX3001]  
MC56F8023MFAE@QFP32 [CX3001]  
MC56F8025VLD@QFP44 [CX3003]  
MC56F8033VLC@QFP32 [CX3001]  
MC56F8036MFAE@QFP48 [CX3007]  
MC56F8037VLH@QFP64 [CX3011]  
MC56F8122MFAE@QFP48 [CX3007]  
MC56F8122VFAE@QFP48 [CX3007]  
MC56F8123MFBE@QFP64 [CX3011]  
MC56F8123VFBE@QFP64 [CX3011]  
MC56F8246VLF@QFP48 [CX3007]  
MC56F8247VLH@QFP64 [CX3011]  
MC56F8256VLF@QFP48 [CX3007]  
MC56F8257VLH@QFP64 [CX3011]  
MC56F8322MFAE@QFP48 [CX3007]  
MC56F8322VFAE@QFP48 [CX3007]  
MC56F8323MFBE@QFP64 [CX3011]  
MC56F8323VFBE@QFP64 [CX3011]  
MC68HC11E1@QFP52 [CX3010]  
MC68HC11E1CFU3 [CX3044]  
MC68HC11E1VFU2 [CX3044]  
MC68HC11E20@QFP52 [CX3010]  
MC68HC11E20CFU3 [CX3044]  
MC68HC11E20VFU2 [CX3044]  
MC68HC11E9@QFP52 [CX3010]  
MC68HC11E9CFU3 [CX3044]  
MC68HC11E9VFU2 [CX3044]  
MC68HC11EA9CFN3 [CX2052]

MC68HC11EA9CFS2 [CX2052]  
MC68HC11EA9MFN2 [CX2052]  
MC68HC11EA9MFS2 [CX2052]  
MC68HC11EA9VFN2 [CX2052]  
MC68HC11EA9VFS2 [CX2052]  
MC68HC11F1@PLCC68 [CX2068]  
MC68HC11F1ACFN2 [CX2068]  
MC68HC11F1ACFN4 [CX2068]  
MC68HC11F1ACPU3 [CX3017]  
MC68HC11F1AMFN2 [CX2068]  
MC68HC11F1AMFN4 [CX2068]  
MC68HC11F1AMPU3 [CX3017]  
MC68HC11F1AVFN2 [CX2068]  
MC68HC11F1AVFN4 [CX2068]  
MC68HC11F1AVPU3 [CX3017]  
MC68HC11F1CFN2 [CX2068]  
MC68HC11F1CFN4 [CX2068]  
MC68HC11F1CPU3 [CX3017]  
MC68HC11F1MFN2 [CX2068]  
MC68HC11F1MFN4 [CX2068]  
MC68HC11F1MPU3 [CX3017]  
MC68HC11F1VFN2 [CX2068]  
MC68HC11F1VFN4 [CX2068]  
MC68HC11F1VPU3 [CX3017]  
MC68HC11K1@PLCC84 [CX2084]  
MC68HC11KS2@PLCC68 [CX2068]  
MC68HC705B16CB [CX0056]  
MC68HC705B16CFU [CX3013]  
MC68HC705B16FU [CX3013]  
MC68HC705B16NCB [CX0056]  
MC68HC705B16NCFU [CX3013]  
MC68HC705B16NFU [CX3013]  
MC68HC705C4@PLCC44 [CX2044]  
MC68HC705C4A@PLCC44 [CX2044]  
MC68HC705C8@PLCC44 [CX2044]  
MC68HC705C8@TQFP44 [CX3002]  
MC68HC705C8A@PLCC44 [CX2044]  
MC68HC705C8A@TQFP44 [CX3002]  
MC68HC705C9A@PLCC44 [CX2044]  
MC68HC705P6(CDW)@SOIC28 [CX1033]  
MC68HC705P6A(CDW)@SOIC28 [CX1033]  
MC68HC705P6A(CP) [CX0001]  
MC68HC705P9@SOIC28 [CX1033]  
MC68HC711E9@PLCC52 [CX2052]  
MC68HC711E9CFN2@PLCC52 [CX2052]  
MC68HC711E9CFNE@PLCC52 [CX2052]  
MC68HC711E9CFNE3@PLCC52 [CX2052]  
MC68HC711E9MFN2@PLCC52 [CX2052]  
MC68HC711E9VFN2@PLCC52 [CX2052]  
MC68HC711EA9CFN2 [CX2052]  
MC68HC711EA9CFS2 [CX2052]  
MC68HC711EA9MFN2 [CX2052]  
MC68HC711EA9MFS2 [CX2052]  
MC68HC711EA9VFN2 [CX2052]  
MC68HC711EA9VFS2 [CX2052]  
MC68HC711K4@PLCC84 [CX2084]  
MC68HC711KA2@PLCC68 [CX2068]  
MC68HC711KA4@PLCC68 [CX2068]  
MC68HC711L6@PLCC68 [CX2068]

MC68HC11EA9CFS3 [CX2052]  
MC68HC11EA9MFN3 [CX2052]  
MC68HC11EA9MFS3 [CX2052]  
MC68HC11EA9VFN3 [CX2052]  
MC68HC11EA9VFS3 [CX2052]  
MC68HC11F1A@PLCC68 [CX2068]  
MC68HC11F1ACFN3 [CX2068]  
MC68HC11F1ACPU2 [CX3017]  
MC68HC11F1ACPU4 [CX3017]  
MC68HC11F1AMFN3 [CX2068]  
MC68HC11F1AMPU2 [CX3017]  
MC68HC11F1AMPU4 [CX3017]  
MC68HC11F1AVFN3 [CX2068]  
MC68HC11F1AVPU2 [CX3017]  
MC68HC11F1AVPU4 [CX3017]  
MC68HC11F1CFN3 [CX2068]  
MC68HC11F1CPU2 [CX3017]  
MC68HC11F1CPU4 [CX3017]  
MC68HC11F1MFN3 [CX2068]  
MC68HC11F1MPU2 [CX3017]  
MC68HC11F1MPU4 [CX3017]  
MC68HC11F1VFN3 [CX2068]  
MC68HC11F1VPU2 [CX3017]  
MC68HC11F1VPU4 [CX3017]  
MC68HC11K1@TQFP80 [CX3018]  
MC68HC705B16B [CX0056]  
MC68HC705B16CFN [CX2052]  
MC68HC705B16FN [CX2052]  
MC68HC705B16NB [CX0056]  
MC68HC705B16NCFN [CX2052]  
MC68HC705B16NFN [CX2052]  
MC68HC705C4 [CX0001]  
MC68HC705C4A [CX0001]  
MC68HC705C8 [CX0001]  
MC68HC705C8@SDIP42 [CX0042]  
MC68HC705C8A [CX0001]  
MC68HC705C8A@SDIP42 [CX0042]  
MC68HC705C9A [CX0001]  
MC68HC705C9A@TQFP44 [CX3002]  
MC68HC705P6(CP) [CX0001]  
MC68HC705P9 [CX0001]  
MC68HC711E20@PLCC52 [CX2052]  
MC68HC711E9CFN@PLCC52 [CX2052]  
MC68HC711E9CFN3@PLCC52 [CX2052]  
MC68HC711E9CFNE2@PLCC52 [CX2052]  
MC68HC711E9FN@PLCC52 [CX2052]  
MC68HC711E9MFNE2@PLCC52 [CX2052]  
MC68HC711E9VFNE2@PLCC52 [CX2052]  
MC68HC711EA9CFN3 [CX2052]  
MC68HC711EA9CFS3 [CX2052]  
MC68HC711EA9MFN3 [CX2052]  
MC68HC711EA9MFS3 [CX2052]  
MC68HC711EA9VFN3 [CX2052]  
MC68HC711EA9VFS3 [CX2052]  
MC68HC711K4@TQFP80 [CX3018]  
MC68HC711KA3@PLCC68 [CX2068]  
MC68HC711KS2@PLCC68 [CX2068]  
MC68HC711L6@TQFP64 [CX3013]

MC68HC811E2 [CX0001]  
MC68HC811E2C [CX0001]  
MC68HC811E2V [CX0001]  
MC68HC908AB32CFUE@TQFP64 [CX3014]  
MC68HC908AB32MFU@TQFP64 [CX3014]  
MC68HC908AB32MFUE@TQFP64 [CX3014]  
MC68HC908AB32VFU@TQFP64 [CX3014]  
MC68HC908AB32VFUE@TQFP64 [CX3014]  
MC68HC908AP16CB@SDIP42 [CX0042]      MC68HC908AP16CBE@SDIP42 [CX0042]  
MC68HC908AP16CFA@LQFP48 [CX3007]  
MC68HC908AP16CFAE@LQFP48 [CX3007]  
MC68HC908AP16CFB@TQFP44 [CX3002]  
MC68HC908AP16CFBE@TQFP44 [CX3002]  
MC68HC908AP16MB@SDIP42 [CX0042]      MC68HC908AP16MBE@SDIP42 [CX0042]  
MC68HC908AP16MFA@LQFP48 [CX3007]  
MC68HC908AP16MFAE@LQFP48 [CX3007]  
MC68HC908AP16MFB@TQFP44 [CX3002]  
MC68HC908AP16MFBE@TQFP44 [CX3002]  
MC68HC908AP16VB@SDIP42 [CX0042]      MC68HC908AP16VBE@SDIP42 [CX0042]  
MC68HC908AP16VFA@LQFP48 [CX3007]  
MC68HC908AP16VFAE@LQFP48 [CX3007]  
MC68HC908AP16VFB@TQFP44 [CX3002]  
MC68HC908AP16VFBE@TQFP44 [CX3002]  
MC68HC908AP32CB@SDIP42 [CX0042]      MC68HC908AP32CBE@SDIP42 [CX0042]  
MC68HC908AP32CFA@LQFP48 [CX3007]  
MC68HC908AP32CFAE@LQFP48 [CX3007]  
MC68HC908AP32CFB@TQFP44 [CX3002]  
MC68HC908AP32CFBE@TQFP44 [CX3002]  
MC68HC908AP32MB@SDIP42 [CX0042]      MC68HC908AP32MBE@SDIP42 [CX0042]  
MC68HC908AP32MFA@LQFP48 [CX3007]  
MC68HC908AP32MFAE@LQFP48 [CX3007]  
MC68HC908AP32MFB@TQFP44 [CX3002]  
MC68HC908AP32MFBE@TQFP44 [CX3002]  
MC68HC908AP32VB@SDIP42 [CX0042]      MC68HC908AP32VBE@SDIP42 [CX0042]  
MC68HC908AP32VFA@LQFP48 [CX3007]  
MC68HC908AP32VFAE@LQFP48 [CX3007]  
MC68HC908AP32VFB@TQFP44 [CX3002]  
MC68HC908AP32VFBE@TQFP44 [CX3002]  
MC68HC908AP64CB@SDIP42 [CX0042]      MC68HC908AP64CBE@SDIP42 [CX0042]  
MC68HC908AP64CFA@LQFP48 [CX3007]  
MC68HC908AP64CFAE@LQFP48 [CX3007]  
MC68HC908AP64CFB@TQFP44 [CX3002]  
MC68HC908AP64CFBE@TQFP44 [CX3002]  
MC68HC908AP64MB@SDIP42 [CX0042]      MC68HC908AP64MBE@SDIP42 [CX0042]  
MC68HC908AP64MFA@LQFP48 [CX3007]  
MC68HC908AP64MFAE@LQFP48 [CX3007]  
MC68HC908AP64MFB@TQFP44 [CX3002]  
MC68HC908AP64MFBE@TQFP44 [CX3002]  
MC68HC908AP64VB@SDIP42 [CX0042]      MC68HC908AP64VBE@SDIP42 [CX0042]  
MC68HC908AP64VFA@LQFP48 [CX3007]  
MC68HC908AP64VFAE@LQFP48 [CX3007]  
MC68HC908AP64VFB@TQFP44 [CX3002]  
MC68HC908AP64VFBE@TQFP44 [CX3002]  
MC68HC908AP8CB@SDIP42 [CX0042]      MC68HC908AP8CBE@SDIP42 [CX0042]  
MC68HC908AP8CFA@LQFP48 [CX3007]      MC68HC908AP8CFAE@LQFP48 [CX3007]  
MC68HC908AP8CFB@TQFP44 [CX3002]      MC68HC908AP8CFBE@TQFP44 [CX3002]  
MC68HC908AP8MB@SDIP42 [CX0042]      MC68HC908AP8MBE@SDIP42 [CX0042]  
MC68HC908AP8MFA@LQFP48 [CX3007]      MC68HC908AP8MFAE@LQFP48 [CX3007]  
MC68HC908AP8MFB@TQFP44 [CX3002]      MC68HC908AP8MFBE@TQFP44 [CX3002]

MC68HC908AP8VB@SDIP42 [CX0042]      MC68HC908AP8VBE@SDIP42 [CX0042]  
MC68HC908AP8VFA@LQFP48 [CX3007]      MC68HC908AP8VFAE@LQFP48 [CX3007]  
MC68HC908AP8VFB@TQFP44 [CX3002]      MC68HC908AP8VFB@TQFP44 [CX3002]  
MC68HC908AS32ACFN@PLCC52 [CX2052]  
MC68HC908AS32ACFNE@PLCC52 [CX2052]  
MC68HC908AS32ACFU@TQFP64 [CX3014]  
MC68HC908AS32ACFUE@TQFP64 [CX3014]  
MC68HC908AS32AMFN@PLCC52 [CX2052]  
MC68HC908AS32AMFNE@PLCC52 [CX2052]  
MC68HC908AS32AMFU@TQFP64 [CX3014]  
MC68HC908AS32AMFUE@TQFP64 [CX3014]  
MC68HC908AS32AVFN@PLCC52 [CX2052]  
MC68HC908AS32AVFNE@PLCC52 [CX2052]  
MC68HC908AS32AVFU@TQFP64 [CX3014]  
MC68HC908AS32AVFUE@TQFP64 [CX3014]  
MC68HC908AS60ACFN@PLCC52 [CX2052]  
MC68HC908AS60ACFU@TQFP64 [CX3014]  
MC68HC908AS60AMFN@PLCC52 [CX2052]  
MC68HC908AS60AMFU@TQFP64 [CX3014]  
MC68HC908AS60AVFN@PLCC52 [CX2052]  
MC68HC908AS60AVFU@TQFP64 [CX3014]  
MC68HC908AS60CFN@PLCC52 [CX2052]      MC68HC908AS60CFU@TQFP64 [CX3014]  
MC68HC908AS60MFN@PLCC52 [CX2052]      MC68HC908AS60MFU@TQFP64 [CX3014]  
MC68HC908AS60VFN@PLCC52 [CX2052]      MC68HC908AS60VFU@TQFP64 [CX3014]  
MC68HC908AZ32ACFU@TQFP64 [CX3014]  
MC68HC908AZ32ACFUE@TQFP64 [CX3014]  
MC68HC908AZ32AMFU@TQFP64 [CX3014]  
MC68HC908AZ32AMFUE@TQFP64 [CX3014]  
MC68HC908AZ32AVFU@TQFP64 [CX3014]  
MC68HC908AZ32AVFUE@TQFP64 [CX3014]  
MC68HC908AZ60ACFU@TQFP64 [CX3014]  
MC68HC908AZ60ACFUE@TQFP64 [CX3014]  
MC68HC908AZ60AMFU@TQFP64 [CX3014]  
MC68HC908AZ60AMFUE@TQFP64 [CX3014]  
MC68HC908AZ60AVFU@TQFP64 [CX3014]  
MC68HC908AZ60AVFUE@TQFP64 [CX3014]  
MC68HC908AZ60CFU@TQFP64 [CX3014]      MC68HC908AZ60MFU@TQFP64 [CX3014]  
MC68HC908AZ60VFU@TQFP64 [CX3014]      MC68HC908BD48IB@SDIP42 [CX0042]  
MC68HC908BD48IB@SDIP42 [CX0042]      MC68HC908BD48IFB@TQFP44 [CX3002]  
MC68HC908BD48IFBE@TQFP44 [CX3002]  
MC68HC908EY16ACFJ@TQFP32 [CX3001]  
MC68HC908EY16ACFJE@TQFP32 [CX3001]  
MC68HC908EY16AKFJ@TQFP32 [CX3001]  
MC68HC908EY16AKFJE@TQFP32 [CX3001]  
MC68HC908EY16AMFJ@TQFP32 [CX3001]  
MC68HC908EY16AMFJE@TQFP32 [CX3001]  
MC68HC908EY16AVFJ@TQFP32 [CX3001]  
MC68HC908EY16AVFJE@TQFP32 [CX3001]  
MC68HC908EY16CFA@TQFP32 [CX3001]  
MC68HC908EY16CFAE@TQFP32 [CX3001]  
MC68HC908EY16KFA@TQFP32 [CX3001]  
MC68HC908EY16KFAE@TQFP32 [CX3001]  
MC68HC908EY16MFA@TQFP32 [CX3001]  
MC68HC908EY16MFAE@TQFP32 [CX3001]  
MC68HC908EY16VFA@TQFP32 [CX3001]  
MC68HC908EY16VFAE@TQFP32 [CX3001]  
MC68HC908EY8ACFJ@TQFP32 [CX3001]  
MC68HC908EY8ACFJE@TQFP32 [CX3001]  
MC68HC908EY8AKFJ@TQFP32 [CX3001]



MC68HC908EY8AKFJE@TQFP32 [CX3001]  
MC68HC908EY8AMFJ@TQFP32 [CX3001]  
MC68HC908EY8AMFJE@TQFP32 [CX3001]  
MC68HC908EY8AVFJ@TQFP32 [CX3001]  
MC68HC908EY8AVFJE@TQFP32 [CX3001]  
MC68HC908EY8CFA@TQFP32 [CX3001] MC68HC908EY8CFAE@TQFP32 [CX3001]  
MC68HC908EY8KFA@TQFP32 [CX3001] MC68HC908EY8KFAE@TQFP32 [CX3001]  
MC68HC908EY8MFA@TQFP32 [CX3001] MC68HC908EY8MFAE@TQFP32 [CX3001]  
MC68HC908EY8VFA@TQFP32 [CX3001] MC68HC908EY8VFAE@TQFP32 [CX3001]  
MC68HC908GP32CB@SDIP42 [CX0042] MC68HC908GP32CBE@SDIP42 [CX0042]  
MC68HC908GP32CFB@TQFP44 [CX3002]  
MC68HC908GP32CFBE@TQFP44 [CX3002]  
MC68HC908GP32CP  
MC68HC908GP32MB@SDIP42 [CX0042] MC68HC908GP32CPE  
MC68HC908GP32MFB@TQFP44 [CX3002] MC68HC908GP32MBE@SDIP42 [CX0042]  
MC68HC908GP32MFBE@TQFP44 [CX3002]  
MC68HC908GP32MP  
MC68HC908GP32VB@SDIP42 [CX0042] MC68HC908GP32MPE  
MC68HC908GP32VFB@TQFP44 [CX3002] MC68HC908GP32VBE@SDIP42 [CX0042]  
MC68HC908GP32VFBE@TQFP44 [CX3002]  
MC68HC908GP32VP  
MC68HC908GP32VPE  
MC68HC908GR16ACFA@TQFP48 [CX3007]  
MC68HC908GR16ACFAE@TQFP48 [CX3007]  
MC68HC908GR16ACFJ@TQFP32 [CX3001]  
MC68HC908GR16ACFJE@TQFP32 [CX3001]  
MC68HC908GR16AMFA@TQFP48 [CX3007]  
MC68HC908GR16AMFAE@TQFP48 [CX3007]  
MC68HC908GR16AMFJ@TQFP32 [CX3001]  
MC68HC908GR16AMFJE@TQFP32 [CX3001]  
MC68HC908GR16AVFA@TQFP48 [CX3007]  
MC68HC908GR16AVFAE@TQFP48 [CX3007]  
MC68HC908GR16AVFJ@TQFP32 [CX3001]  
MC68HC908GR16AVFJE@TQFP32 [CX3001]  
MC68HC908GR16CFA@TQFP48 [CX3007]  
MC68HC908GR16CFAE@TQFP48 [CX3007]  
MC68HC908GR16CFJ@TQFP32 [CX3001]  
MC68HC908GR16CFJE@TQFP32 [CX3001]  
MC68HC908GR16MFA@TQFP48 [CX3007]  
MC68HC908GR16MFAE@TQFP48 [CX3007]  
MC68HC908GR16MFJ@TQFP32 [CX3001]  
MC68HC908GR16MFJE@TQFP32 [CX3001]  
MC68HC908GR16VFA@TQFP48 [CX3007]  
MC68HC908GR16VFAE@TQFP48 [CX3007]  
MC68HC908GR16VFJ@TQFP32 [CX3001]  
MC68HC908GR16VFJE@TQFP32 [CX3001]  
MC68HC908GR32ACFA@TQFP48 [CX3007]  
MC68HC908GR32ACFAE@TQFP48 [CX3007]  
MC68HC908GR32ACFJ@TQFP32 [CX3001]  
MC68HC908GR32ACFJE@TQFP32 [CX3001]  
MC68HC908GR32ACFU@QFP64 [CX3014]  
MC68HC908GR32ACFUE@QFP64 [CX3014]  
MC68HC908GR32AMFA@TQFP48 [CX3007]  
MC68HC908GR32AMFAE@TQFP48 [CX3007]  
MC68HC908GR32AMFJ@TQFP32 [CX3001]  
MC68HC908GR32AMFJE@TQFP32 [CX3001]  
MC68HC908GR32AMFU@QFP64 [CX3014]  
MC68HC908GR32AMFUE@QFP64 [CX3014]  
MC68HC908GR32AVFA@TQFP48 [CX3007]  
MC68HC908GR32AVFAE@TQFP48 [CX3007]

MC68HC908GR32AVFJ@TQFP32 [CX3001]  
MC68HC908GR32AVFJE@TQFP32 [CX3001]  
MC68HC908GR32AVFU@QFP64 [CX3014]  
MC68HC908GR32AVFUE@QFP64 [CX3014]  
MC68HC908GR48ACFA@TQFP48 [CX3007]  
MC68HC908GR48ACFAE@TQFP48 [CX3007]  
MC68HC908GR48ACFJ@TQFP32 [CX3001]  
MC68HC908GR48ACFJE@TQFP32 [CX3001]  
MC68HC908GR48ACFU@QFP64 [CX3014]  
MC68HC908GR48ACFUE@QFP64 [CX3014]  
MC68HC908GR48AMFA@TQFP48 [CX3007]  
MC68HC908GR48AMFAE@TQFP48 [CX3007]  
MC68HC908GR48AMFJ@TQFP32 [CX3001]  
MC68HC908GR48AMFJE@TQFP32 [CX3001]  
MC68HC908GR48AMFU@QFP64 [CX3014]  
MC68HC908GR48AMFUE@QFP64 [CX3014]  
MC68HC908GR48AVFA@TQFP48 [CX3007]  
MC68HC908GR48AVFAE@TQFP48 [CX3007]  
MC68HC908GR48AVFJ@TQFP32 [CX3001]  
MC68HC908GR48AVFJE@TQFP32 [CX3001]  
MC68HC908GR48AVFU@QFP64 [CX3014]  
MC68HC908GR48AVFUE@QFP64 [CX3014]  
MC68HC908GR4ACDW@SOIC28 [CX1033]  
MC68HC908GR4ACDWE@SOIC28 [CX1033]  
MC68HC908GR4ACFA@TQFP32 [CX3001]  
MC68HC908GR4ACFAE@TQFP32 [CX3001]  
MC68HC908GR4ACP  
MC68HC908GR4AMDW@SOIC28 [CX1033]  
MC68HC908GR4AMDWE@SOIC28 [CX1033]  
MC68HC908GR4AMFA@TQFP32 [CX3001]  
MC68HC908GR4AMFAE@TQFP32 [CX3001]  
MC68HC908GR4AMP  
MC68HC908GR4AVDW@SOIC28 [CX1033]  
MC68HC908GR4AVDWE@SOIC28 [CX1033]  
MC68HC908GR4AVFA@TQFP32 [CX3001]  
MC68HC908GR4AVFAE@TQFP32 [CX3001]  
MC68HC908GR4AVP  
MC68HC908GR4CB@SDIP42 [CX0042]  
MC68HC908GR4CDW@SOIC28 [CX1033]  
MC68HC908GR4CFA@TQFP32 [CX3001]  
MC68HC908GR4CP  
MC68HC908GR4MB@SDIP42 [CX0042]  
MC68HC908GR4MDW@SOIC28 [CX1033]  
MC68HC908GR4MFA@TQFP32 [CX3001]  
MC68HC908GR4MP  
MC68HC908GR4VB@SDIP42 [CX0042]  
MC68HC908GR4VDW@SOIC28 [CX1033]  
MC68HC908GR4VFA@TQFP32 [CX3001]  
MC68HC908GR4VP  
MC68HC908GR60ACFA@TQFP48 [CX3007]  
MC68HC908GR60ACFAE@TQFP48 [CX3007]  
MC68HC908GR60ACFJ@TQFP32 [CX3001]  
MC68HC908GR60ACFJE@TQFP32 [CX3001]  
MC68HC908GR60ACFU@QFP64 [CX3014]  
MC68HC908GR60ACFUE@QFP64 [CX3014]  
MC68HC908GR60AMFA@TQFP48 [CX3007]  
MC68HC908GR60AMFAE@TQFP48 [CX3007]  
MC68HC908GR60AMFJ@TQFP32 [CX3001]  
MC68HC908GR60AMFJE@TQFP32 [CX3001]

MC68HC908GR4ACPE

MC68HC908GR4AMPE

MC68HC908GR4AVPE

MC68HC908GR4CBE@SDIP42 [CX0042]  
MC68HC908GR4CDWE@SOIC28 [CX1033]  
MC68HC908GR4CFAE@TQFP32 [CX3001]  
MC68HC908GR4CPE  
MC68HC908GR4MBE@SDIP42 [CX0042]  
MC68HC908GR4MDWE@SOIC28 [CX1033]  
MC68HC908GR4MFAE@TQFP32 [CX3001]  
MC68HC908GR4MPE  
MC68HC908GR4VBE@SDIP42 [CX0042]  
MC68HC908GR4VDWE@SOIC28 [CX1033]  
MC68HC908GR4VFAE@TQFP32 [CX3001]  
MC68HC908GR4VPE

MC68HC908GR60AMFU@QFP64 [CX3014]  
MC68HC908GR60AMFUE@QFP64 [CX3014]  
MC68HC908GR60AVFA@TQFP48 [CX3007]  
MC68HC908GR60AVFAE@TQFP48 [CX3007]  
MC68HC908GR60AVFJ@TQFP32 [CX3001]  
MC68HC908GR60AVFJE@TQFP32 [CX3001]  
MC68HC908GR60AVFU@QFP64 [CX3014]  
MC68HC908GR60AVFUE@QFP64 [CX3014]  
MC68HC908GR8ACDW@SOIC28 [CX1033]  
MC68HC908GR8ACDWE@SOIC28 [CX1033]  
MC68HC908GR8ACFA@TQFP32 [CX3001]  
MC68HC908GR8ACFAE@TQFP32 [CX3001]  
MC68HC908GR8ACP  
MC68HC908GR8AMDW@SOIC28 [CX1033]  
MC68HC908GR8AMDWE@SOIC28 [CX1033]  
MC68HC908GR8AMFA@TQFP32 [CX3001]  
MC68HC908GR8AMFAE@TQFP32 [CX3001]  
MC68HC908GR8AMP  
MC68HC908GR8AVDW@SOIC28 [CX1033]  
MC68HC908GR8AVDWE@SOIC28 [CX1033]  
MC68HC908GR8AVFA@TQFP32 [CX3001]  
MC68HC908GR8AVFAE@TQFP32 [CX3001]  
MC68HC908GR8AVP  
MC68HC908GR8CB@SDIP42 [CX0042]  
MC68HC908GR8CDW@SOIC28 [CX1033]  
MC68HC908GR8CFA@TQFP32 [CX3001]  
MC68HC908GR8CP  
MC68HC908GR8MB@SDIP42 [CX0042]  
MC68HC908GR8MDW@SOIC28 [CX1033]  
MC68HC908GR8MFA@TQFP32 [CX3001]  
MC68HC908GR8MP  
MC68HC908GR8VB@SDIP42 [CX0042]  
MC68HC908GR8VDW@SOIC28 [CX1033]  
MC68HC908GR8VFA@TQFP32 [CX3001]  
MC68HC908GR8VP  
MC68HC908GT16CB@SDIP42 [CX0042]  
MC68HC908GT16CFB@TQFP44 [CX3002]  
MC68HC908GT16CFBE@TQFP44 [CX3002]  
MC68HC908GT16MB@SDIP42 [CX0042]  
MC68HC908GT16MFB@TQFP44 [CX3002]  
MC68HC908GT16MFBE@TQFP44 [CX3002]  
MC68HC908GT16VB@SDIP42 [CX0042]  
MC68HC908GT16VFB@TQFP44 [CX3002]  
MC68HC908GT16VFBE@TQFP44 [CX3002]  
MC68HC908GT8CB@SDIP42 [CX0042]  
MC68HC908GT8CFB@TQFP44 [CX3002]  
MC68HC908GT8MB@SDIP42 [CX0042]  
MC68HC908GT8MFB@TQFP44 [CX3002]  
MC68HC908GT8VFB@TQFP44 [CX3002]  
MC68HC908GT8VBE@TQFP44 [CX3002]  
MC68HC908GT8VFB@TQFP44 [CX3002]  
MC68HC908GZ16CFA@TQFP48 [CX3007]  
MC68HC908GZ16CFAE@TQFP48 [CX3007]  
MC68HC908GZ16CFJ@TQFP32 [CX3001]  
MC68HC908GZ16CFJE@TQFP32 [CX3001]  
MC68HC908GZ16MFA@TQFP48 [CX3007]  
MC68HC908GZ16MFAE@TQFP48 [CX3007]  
MC68HC908GZ16MFJ@TQFP32 [CX3001]  
MC68HC908GZ16MFJE@TQFP32 [CX3001]  
MC68HC908GZ16VFA@TQFP48 [CX3007]

MC68HC908GR8ACPE  
  
MC68HC908GR8AMPE  
  
MC68HC908GR8AVPE  
MC68HC908GR8CBE@SDIP42 [CX0042]  
MC68HC908GR8CDWE@SOIC28 [CX1033]  
MC68HC908GR8CFAE@TQFP32 [CX3001]  
MC68HC908GR8CPE  
MC68HC908GR8MBE@SDIP42 [CX0042]  
MC68HC908GR8MDWE@SOIC28 [CX1033]  
MC68HC908GR8MFAE@TQFP32 [CX3001]  
MC68HC908GR8MPE  
MC68HC908GR8VBE@SDIP42 [CX0042]  
MC68HC908GR8VDWE@SOIC28 [CX1033]  
MC68HC908GR8VFAE@TQFP32 [CX3001]  
MC68HC908GR8VPE  
MC68HC908GT16CBE@SDIP42 [CX0042]  
  
MC68HC908GT16MBE@SDIP42 [CX0042]  
  
MC68HC908GT16VBE@SDIP42 [CX0042]  
  
MC68HC908GT8CBE@SDIP42 [CX0042]  
MC68HC908GT8CFBE@TQFP44 [CX3002]  
MC68HC908GT8MBE@SDIP42 [CX0042]  
MC68HC908GT8MFBE@TQFP44 [CX3002]  
MC68HC908GT8VBE@SDIP42 [CX0042]  
MC68HC908GT8VFBE@TQFP44 [CX3002]

MC68HC908GZ16VFAE@TQFP48 [CX3007]  
MC68HC908GZ16VFJ@TQFP32 [CX3001]  
MC68HC908GZ16VFJE@TQFP32 [CX3001]  
MC68HC908GZ32CFA@TQFP48 [CX3007]  
MC68HC908GZ32CFAE@TQFP48 [CX3007]  
MC68HC908GZ32CFJ@TQFP32 [CX3001]  
MC68HC908GZ32CFJE@TQFP32 [CX3001]  
MC68HC908GZ32CFU@QFP64 [CX3014] MC68HC908GZ32CFUE@QFP64 [CX3014]  
MC68HC908GZ32MFA@TQFP48 [CX3007]  
MC68HC908GZ32MFAE@TQFP48 [CX3007]  
MC68HC908GZ32MFJ@TQFP32 [CX3001]  
MC68HC908GZ32MFJE@TQFP32 [CX3001]  
MC68HC908GZ32MFU@QFP64 [CX3014] MC68HC908GZ32MFUE@QFP64 [CX3014]  
MC68HC908GZ32VFA@TQFP48 [CX3007]  
MC68HC908GZ32VFAE@TQFP48 [CX3007]  
MC68HC908GZ32VFJ@TQFP32 [CX3001]  
MC68HC908GZ32VFJE@TQFP32 [CX3001]  
MC68HC908GZ32VFU@QFP64 [CX3014] MC68HC908GZ32VFUE@QFP64 [CX3014]  
MC68HC908GZ48CFA@TQFP48 [CX3007]  
MC68HC908GZ48CFAE@TQFP48 [CX3007]  
MC68HC908GZ48CFJ@TQFP32 [CX3001]  
MC68HC908GZ48CFJE@TQFP32 [CX3001]  
MC68HC908GZ48CFU@QFP64 [CX3014] MC68HC908GZ48CFUE@QFP64 [CX3014]  
MC68HC908GZ48MFA@TQFP48 [CX3007]  
MC68HC908GZ48MFAE@TQFP48 [CX3007]  
MC68HC908GZ48MFJ@TQFP32 [CX3001]  
MC68HC908GZ48MFJE@TQFP32 [CX3001]  
MC68HC908GZ48MFU@QFP64 [CX3014] MC68HC908GZ48MFUE@QFP64 [CX3014]  
MC68HC908GZ48VFA@TQFP48 [CX3007]  
MC68HC908GZ48VFAE@TQFP48 [CX3007]  
MC68HC908GZ48VFJ@TQFP32 [CX3001]  
MC68HC908GZ48VFJE@TQFP32 [CX3001]  
MC68HC908GZ48VFU@QFP64 [CX3014] MC68HC908GZ48VFUE@QFP64 [CX3014]  
MC68HC908GZ60CFA@TQFP48 [CX3007]  
MC68HC908GZ60CFAE@TQFP48 [CX3007]  
MC68HC908GZ60CFJ@TQFP32 [CX3001]  
MC68HC908GZ60CFJE@TQFP32 [CX3001]  
MC68HC908GZ60CFU@QFP64 [CX3014] MC68HC908GZ60CFUE@QFP64 [CX3014]  
MC68HC908GZ60MFA@TQFP48 [CX3007]  
MC68HC908GZ60MFAE@TQFP48 [CX3007]  
MC68HC908GZ60MFJ@TQFP32 [CX3001]  
MC68HC908GZ60MFJE@TQFP32 [CX3001]  
MC68HC908GZ60MFU@QFP64 [CX3014] MC68HC908GZ60MFUE@QFP64 [CX3014]  
MC68HC908GZ60VFA@TQFP48 [CX3007]  
MC68HC908GZ60VFAE@TQFP48 [CX3007]  
MC68HC908GZ60VFJ@TQFP32 [CX3001]  
MC68HC908GZ60VFJE@TQFP32 [CX3001]  
MC68HC908GZ60VFU@QFP64 [CX3014] MC68HC908GZ60VFUE@QFP64 [CX3014]  
MC68HC908GZ8CFA@TQFP48 [CX3007]  
MC68HC908GZ8CFJ@TQFP32 [CX3001]  
MC68HC908GZ8CFJE@TQFP32 [CX3001]  
MC68HC908GZ8MFA@TQFP48 [CX3007]  
MC68HC908GZ8MFJ@TQFP32 [CX3001]  
MC68HC908GZ8MFJE@TQFP32 [CX3001]  
MC68HC908GZ8VFJ@TQFP32 [CX3001]  
MC68HC908GZ8VFJE@TQFP32 [CX3001]  
MC68HC908GZ8VFUE@QFP64 [CX3014]  
MC68HC908GZ8VFA@TQFP48 [CX3007]  
MC68HC908GZ8VFAE@TQFP48 [CX3007]  
MC68HC908GZ8VFJ@TQFP32 [CX3001]  
MC68HC908GZ8VFJE@TQFP32 [CX3001]  
MC68HC908GZ8VFUE@QFP64 [CX3014]  
MC68HC908GZ8VFAE@TQFP48 [CX3007]  
MC68HC908JB12DW@SOIC28 [CX1033]  
MC68HC908JB12JDW@SOIC20 [CX1033]  
MC68HC908JB12JDWE@SOIC20 [CX1033]  
MC68HC908JB16DW@SOIC28 [CX1033]  
MC68HC908JB16FA@QFP32 [CX3001] MC68HC908JB16DWE@SOIC28 [CX1033]  
MC68HC908JB16FAE@QFP32 [CX3001]

MC68HC908JB16JDW@SOIC20 [CX1033]  
MC68HC908JB16JDWE@SOIC20 [CX1033]  
MC68HC908JB8ADW@SOIC28 [CX1033]  
MC68HC908JB8FB@TQFP44 [CX3003]  
MC68HC908JB8JDW@SOIC20 [CX1033]  
MC68HC908JB8JP  
MC68HC908JK1CDW@SOIC20 [CX1033]  
MC68HC908JK1CP  
MC68HC908JK1ECDW@SOIC20 [CX1033]  
MC68HC908JK1ECDWE@SOIC20 [CX1033]  
MC68HC908JK1ECP  
MC68HC908JK1EMDW@SOIC20 [CX1033]  
MC68HC908JK1EMDWE@SOIC20 [CX1033]  
MC68HC908JK1EMP  
MC68HC908JK1EVDW@SOIC20 [CX1033]  
MC68HC908JK1EVDWE@SOIC20 [CX1033]  
MC68HC908JK1EVP  
MC68HC908JK1MDW@SOIC20 [CX1033]  
MC68HC908JK1MP  
MC68HC908JK1VDW@SOIC20 [CX1033]  
MC68HC908JK1VP  
MC68HC908JK3CDW@SOIC20 [CX1033]  
MC68HC908JK3CP  
MC68HC908JK3ECDW@SOIC20 [CX1033]  
MC68HC908JK3ECDWE@SOIC20 [CX1033]  
MC68HC908JK3ECP  
MC68HC908JK3EMDW@SOIC20 [CX1033]  
MC68HC908JK3EMDWE@SOIC20 [CX1033]  
MC68HC908JK3EMP  
MC68HC908JK3EVDW@SOIC20 [CX1033]  
MC68HC908JK3EVDWE@SOIC20 [CX1033]  
MC68HC908JK3EVP  
MC68HC908JK3MDW@SOIC20 [CX1033]  
MC68HC908JK3MP  
MC68HC908JK3VDW@SOIC20 [CX1033]  
MC68HC908JK3VP  
MC68HC908JK8CDW@SOIC20 [CX1033]  
MC68HC908JK8CP  
MC68HC908JK8MDW@SOIC20 [CX1033]  
MC68HC908JK8MP  
MC68HC908JK8VDW@SOIC20 [CX1033]  
MC68HC908JK8VP  
MC68HC908JL16CDW@SOIC28 [CX1033]  
MC68HC908JL16CDWE@SOIC28 [CX1033]  
MC68HC908JL16CFJ@TQFP32 [CX3001]  
MC68HC908JL16CFJE@TQFP32 [CX3001]  
MC68HC908JL16CP  
MC68HC908JL16CSP@SDIP32 [CX0032]  
MC68HC908JL16CSPE@SDIP32 [CX0032]  
MC68HC908JL16MDW@SOIC28 [CX1033]  
MC68HC908JL16MDWE@SOIC28 [CX1033]  
MC68HC908JL16MFJ@TQFP32 [CX3001]  
MC68HC908JL16MFJE@TQFP32 [CX3001]  
MC68HC908JL16MP  
MC68HC908JL16MSP@SDIP32 [CX0032]  
MC68HC908JL16MSPE@SDIP32 [CX0032]  
MC68HC908JL16VDW@SOIC28 [CX1033]  
MC68HC908JL16VDWE@SOIC28 [CX1033]  
MC68HC908JL16VFJ@TQFP32 [CX3001]

MC68HC908JB8ADWE@SOIC28 [CX1033]  
MC68HC908JB8FBE@TQFP44 [CX3003]  
MC68HC908JB8JDWE@SOIC20 [CX1033]  
MC68HC908JB8JPE  
MC68HC908JK1CDWE@SOIC20 [CX1033]  
MC68HC908JK1CPE

MC68HC908JK1ECPE

MC68HC908JK1EMPE

MC68HC908JK1EVPE  
MC68HC908JK1MDWE@SOIC20 [CX1033]  
MC68HC908JK1MPE  
MC68HC908JK1VDWE@SOIC20 [CX1033]  
MC68HC908JK1VPE  
MC68HC908JK3CDWE@SOIC20 [CX1033]  
MC68HC908JK3CPE

MC68HC908JK3ECPE

MC68HC908JK3EMPE

MC68HC908JK3EVPE  
MC68HC908JK3MDWE@SOIC20 [CX1033]  
MC68HC908JK3MPE  
MC68HC908JK3VDWE@SOIC20 [CX1033]  
MC68HC908JK3VPE  
MC68HC908JK8CDWE@SOIC20 [CX1033]  
MC68HC908JK8CPE  
MC68HC908JK8MDWE@SOIC20 [CX1033]  
MC68HC908JK8MPE  
MC68HC908JK8VDWE@SOIC20 [CX1033]  
MC68HC908JK8VPE

MC68HC908JL16CPE

MC68HC908JL16MPE

MC68HC908JL16VFJE@TQFP32 [CX3001]	
MC68HC908JL16VP	MC68HC908JL16VPE
MC68HC908JL16VSP@SDIP32 [CX0032]	
MC68HC908JL16VSPE@SDIP32 [CX0032]	
MC68HC908JL3CDW@SOIC28 [CX1033]	MC68HC908JL3CDWE@SOIC28 [CX1033]
MC68HC908JL3CP	MC68HC908JL3CPE
MC68HC908JL3ECDW@SOIC28 [CX1033]	
MC68HC908JL3ECDWE@SOIC28 [CX1033]	
MC68HC908JL3ECFA@TQFP48 [CX3007]	
MC68HC908JL3ECFAE@TQFP48 [CX3007]	
MC68HC908JL3ECP	MC68HC908JL3ECPE
MC68HC908JL3EMDW@SOIC28 [CX1033]	
MC68HC908JL3EMDWE@SOIC28 [CX1033]	
MC68HC908JL3EMFA@TQFP48 [CX3007]	
MC68HC908JL3EMFAE@TQFP48 [CX3007]	
MC68HC908JL3EMP	MC68HC908JL3EMPE
MC68HC908JL3EVDW@SOIC28 [CX1033]	
MC68HC908JL3EVDWE@SOIC28 [CX1033]	
MC68HC908JL3EVFA@TQFP48 [CX3007]	
MC68HC908JL3EVFAE@TQFP48 [CX3007]	
MC68HC908JL3EVP	MC68HC908JL3EVPE
MC68HC908JL3MDW@SOIC28 [CX1033]	MC68HC908JL3MDWE@SOIC28 [CX1033]
MC68HC908JL3MP	MC68HC908JL3MPPE
MC68HC908JL3VDW@SOIC28 [CX1033]	MC68HC908JL3VDWE@SOIC28 [CX1033]
MC68HC908JL3VP	MC68HC908JL3VPE
MC68HC908JL8CDW@SOIC28 [CX1033]	MC68HC908JL8CDWE@SOIC28 [CX1033]
MC68HC908JL8CFA@TQFP32 [CX3001]	MC68HC908JL8CFAE@TQFP32 [CX3001]
MC68HC908JL8CP	MC68HC908JL8CPE
MC68HC908JL8CSP@SDIP32 [CX0032]	MC68HC908JL8CSPE@SDIP32 [CX0032]
MC68HC908JL8MDW@SOIC28 [CX1033]	MC68HC908JL8MDWE@SOIC28 [CX1033]
MC68HC908JL8MFA@TQFP32 [CX3001]	MC68HC908JL8MFAE@TQFP32 [CX3001]
MC68HC908JL8MP	MC68HC908JL8MPPE
MC68HC908JL8MSP@SDIP32 [CX0032]	MC68HC908JL8MSPE@SDIP32 [CX0032]
MC68HC908JL8VDW@SOIC28 [CX1033]	MC68HC908JL8VDWE@SOIC28 [CX1033]
MC68HC908JL8VFA@TQFP32 [CX3001]	MC68HC908JL8VFAE@TQFP32 [CX3001]
MC68HC908JL8VP	MC68HC908JL8VPE
MC68HC908JL8VSP@SDIP32 [CX0032]	MC68HC908JL8VSPE@SDIP32 [CX0032]
MC68HC908KK3ECDW@SOIC20 [CX1033]	
MC68HC908KK3ECDWE@SOIC20 [CX1033]	
MC68HC908KK3ECP	MC68HC908KK3ECPE
MC68HC908KK3EMDW@SOIC20 [CX1033]	
MC68HC908KK3EMDWE@SOIC20 [CX1033]	
MC68HC908KK3EMP	MC68HC908KK3EMPE
MC68HC908KK3EVDW@SOIC20 [CX1033]	
MC68HC908KK3EVDWE@SOIC20 [CX1033]	
MC68HC908KK3EVP	MC68HC908KK3EVPE
MC68HC908KL3ECDW@SOIC28 [CX1033]	
MC68HC908KL3ECDWE@SOIC28 [CX1033]	
MC68HC908KL3ECP	MC68HC908KL3ECPE
MC68HC908KL3EMDW@SOIC28 [CX1033]	
MC68HC908KL3EMDWE@SOIC28 [CX1033]	
MC68HC908KL3EMP	MC68HC908KL3EMPE
MC68HC908KL3EVDW@SOIC28 [CX1033]	
MC68HC908KL3EVDWE@SOIC28 [CX1033]	
MC68HC908KL3EVP	MC68HC908KL3EVPE
MC68HC908KL8CDW@SOIC28 [CX1033]	MC68HC908KL8CDWE@SOIC28 [CX1033]
MC68HC908KL8CP	MC68HC908KL8CPE
MC68HC908KL8CSP@SDIP32 [CX0032]	MC68HC908KL8CSPE@SDIP32 [CX0032]
MC68HC908KL8MDW@SOIC28 [CX1033]	MC68HC908KL8MDWE@SOIC28 [CX1033]

MC68HC908KL8MP  
MC68HC908KL8MSP@SDIP32 [CX0032]  
MC68HC908KL8VDW@SOIC28 [CX1033]  
MC68HC908KL8VP  
MC68HC908KL8VSP@SDIP32 [CX0032]  
MC68HC908KX2CDW@SOIC16 [CX1033]  
MC68HC908KX2CP  
MC68HC908KX2MDW@SOIC16 [CX1033]  
MC68HC908KX2MP  
MC68HC908KX2VDW@SOIC16 [CX1033]  
MC68HC908KX8CDW@SOIC16 [CX1033]  
MC68HC908KX8CP  
MC68HC908KX8MDW@SOIC16 [CX1033]  
MC68HC908KX8MP  
MC68HC908KX8VDW@SOIC16 [CX1033]  
MC68HC908KX8VP  
MC68HC908KXVMP  
MC68HC908LB8CDW@SOIC20 [CX1033]  
MC68HC908LB8CP  
MC68HC908LB8MDW@SOIC20 [CX1033]  
MC68HC908LB8MP  
MC68HC908LB8VDW@SOIC20 [CX1033]  
MC68HC908LB8VP  
MC68HC908LD60IFU@QFP64 [CX3014]  
MC68HC908LJ12CFB@TQFP52 [CX3010]  
MC68HC908LJ12CFBE@TQFP52 [CX3010]  
MC68HC908LJ12CFU@TQFP64 [CX3014]  
MC68HC908LJ12CFUE@TQFP64 [CX3014]  
MC68HC908LJ12CPB@TQFP64 [CX3011]  
MC68HC908LJ12CPBE@TQFP64 [CX3011]  
MC68HC908LJ12MFB@TQFP52 [CX3010]  
MC68HC908LJ12MFBE@TQFP52 [CX3010]  
MC68HC908LJ12MFU@TQFP64 [CX3014]  
MC68HC908LJ12MFUE@TQFP64 [CX3014]  
MC68HC908LJ12MPB@TQFP64 [CX3011]  
MC68HC908LJ12MPBE@TQFP64 [CX3011]  
MC68HC908LJ12VFB@TQFP52 [CX3010]  
MC68HC908LJ12VFBE@TQFP52 [CX3010]  
MC68HC908LJ12VFU@TQFP64 [CX3014]  
MC68HC908LJ12VFUE@TQFP64 [CX3014]  
MC68HC908LJ12VPB@TQFP64 [CX3011]  
MC68HC908LJ12VPBE@TQFP64 [CX3011]  
MC68HC908LJ24CFQ@TQFP80 [CX3018]  
MC68HC908LJ24CFQE@TQFP80 [CX3018]  
MC68HC908LJ24CFU@TQFP64 [CX3014]  
MC68HC908LJ24CFUE@TQFP64 [CX3014]  
MC68HC908LJ24CPB@TQFP64 [CX3011]  
MC68HC908LJ24CPBE@TQFP64 [CX3011]  
MC68HC908LJ24CPK@TQFP80 [CX3016]  
MC68HC908LJ24CPKE@TQFP80 [CX3016]  
MC68HC908LJ24MFQ@TQFP80 [CX3018]  
MC68HC908LJ24MFQE@TQFP80 [CX3018]  
MC68HC908LJ24MFU@TQFP64 [CX3014]  
MC68HC908LJ24MFUE@TQFP64 [CX3014]  
MC68HC908LJ24MPB@TQFP64 [CX3011]  
MC68HC908LJ24MPBE@TQFP64 [CX3011]  
MC68HC908LJ24MPK@TQFP80 [CX3016]  
MC68HC908LJ24MPKE@TQFP80 [CX3016]  
MC68HC908LJ24VFQ@TQFP80 [CX3018]

MC68HC908KL8MPPE  
MC68HC908KL8MSPE@SDIP32 [CX0032]  
MC68HC908KL8VDWE@SOIC28 [CX1033]  
MC68HC908KL8VPPE  
MC68HC908KL8VSPE@SDIP32 [CX0032]  
MC68HC908KX2CDWE@SOIC16 [CX1033]  
MC68HC908KX2CPE  
MC68HC908KX2MDWE@SOIC16 [CX1033]  
MC68HC908KX2MPE  
MC68HC908KX2VDWE@SOIC16 [CX1033]  
MC68HC908KX8CDWE@SOIC16 [CX1033]  
MC68HC908KX8CPE  
MC68HC908KX8MDWE@SOIC16 [CX1033]  
MC68HC908KX8MPE  
MC68HC908KX8VDWE@SOIC16 [CX1033]  
MC68HC908KX8VPE  
MC68HC908KXVMPE  
MC68HC908LB8CDWE@SOIC20 [CX1033]  
MC68HC908LB8CPE  
MC68HC908LB8MDWE@SOIC20 [CX1033]  
MC68HC908LB8MPE  
MC68HC908LB8VDWE@SOIC20 [CX1033]  
MC68HC908LB8VPE  
MC68HC908LD64IFU@QFP64 [CX3014]

MC68HC908LJ24VFQE@TQFP80 [CX3018]  
MC68HC908LJ24VFU@TQFP64 [CX3014]  
MC68HC908LJ24VFUE@TQFP64 [CX3014]  
MC68HC908LJ24VPB@TQFP64 [CX3011]  
MC68HC908LJ24VPBE@TQFP64 [CX3011]  
MC68HC908LJ24VPK@TQFP80 [CX3016]  
MC68HC908LJ24VPKE@TQFP80 [CX3016]  
MC68HC908LK24CFQ@TQFP80 [CX3018]  
MC68HC908LK24CFQE@TQFP80 [CX3018]  
MC68HC908LK24CFU@TQFP64 [CX3014]  
MC68HC908LK24CFUE@TQFP64 [CX3014]  
MC68HC908LK24CPB@TQFP64 [CX3011]  
MC68HC908LK24CPBE@TQFP64 [CX3011]  
MC68HC908LK24CPK@TQFP80 [CX3016]  
MC68HC908LK24CPKE@TQFP80 [CX3016]  
MC68HC908LK24MFQ@TQFP80 [CX3018]  
MC68HC908LK24MFQE@TQFP80 [CX3018]  
MC68HC908LK24MFU@TQFP64 [CX3014]  
MC68HC908LK24MFUE@TQFP64 [CX3014]  
MC68HC908LK24MPB@TQFP64 [CX3011]  
MC68HC908LK24MPBE@TQFP64 [CX3011]  
MC68HC908LK24MPK@TQFP80 [CX3016]  
MC68HC908LK24MPKE@TQFP80 [CX3016]  
MC68HC908LK24VFQ@TQFP80 [CX3018]  
MC68HC908LK24VFQE@TQFP80 [CX3018]  
MC68HC908LK24VFU@TQFP64 [CX3014]  
MC68HC908LK24VFUE@TQFP64 [CX3014]  
MC68HC908LK24VPB@TQFP64 [CX3011]  
MC68HC908LK24VPBE@TQFP64 [CX3011]  
MC68HC908LK24VPK@TQFP80 [CX3016]  
MC68HC908LK24VPKE@TQFP80 [CX3016]  
MC68HC908LV8CPB@TQFP52 [CX3010] MC68HC908LV8CPBE@TQFP52 [CX3010]  
MC68HC908MR16CB@SDIP56 [CX0056] MC68HC908MR16CBE@SDIP56 [CX0056]  
MC68HC908MR16CFU@TQFP64 [CX3014]  
MC68HC908MR16CFUE@TQFP64 [CX3014]  
MC68HC908MR16MB@SDIP56 [CX0056] MC68HC908MR16MBE@SDIP56 [CX0056]  
MC68HC908MR16MFU@TQFP64 [CX3014]  
MC68HC908MR16MFUE@TQFP64 [CX3014]  
MC68HC908MR16VB@SDIP56 [CX0056] MC68HC908MR16VBE@SDIP56 [CX0056]  
MC68HC908MR16VFU@TQFP64 [CX3014]  
MC68HC908MR16VFUE@TQFP64 [CX3014]  
MC68HC908MR32CB@SDIP56 [CX0056] MC68HC908MR32CBE@SDIP56 [CX0056]  
MC68HC908MR32CFU@TQFP64 [CX3014]  
MC68HC908MR32CFUE@TQFP64 [CX3014]  
MC68HC908MR32MB@SDIP56 [CX0056] MC68HC908MR32MBE@SDIP56 [CX0056]  
MC68HC908MR32MFU@TQFP64 [CX3014]  
MC68HC908MR32MFUE@TQFP64 [CX3014]  
MC68HC908MR32VB@SDIP56 [CX0056] MC68HC908MR32VBE@SDIP56 [CX0056]  
MC68HC908MR32VFU@TQFP64 [CX3014]  
MC68HC908MR32VFUE@TQFP64 [CX3014]  
MC68HC908MR8CDW@SOIC28 [CX1033] MC68HC908MR8CDWE@SOIC28 [CX1033]  
MC68HC908MR8CFA@QFP32 [CX3001] MC68HC908MR8CFAE@QFP32 [CX3001]  
MC68HC908MR8CP MC68HC908MR8CPE  
MC68HC908MR8MDW@SOIC28 [CX1033] MC68HC908MR8MDWE@SOIC28 [CX1033]  
MC68HC908MR8MFA@QFP32 [CX3001] MC68HC908MR8MFAE@QFP32 [CX3001]  
MC68HC908MR8MP MC68HC908MR8MPE  
MC68HC908MR8VDW@SOIC28 [CX1033] MC68HC908MR8VDWE@SOIC28 [CX1033]  
MC68HC908MR8VFA@QFP32 [CX3001] MC68HC908MR8VFAE@QFP32 [CX3001]  
MC68HC908MR8VP MC68HC908MR8VPE



MC68HC908QB4CDT@TSSOP16 [CX1001]  
MC68HC908QB4CDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB4CDTE@TSSOP16 [CX1001]  
MC68HC908QB4CDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB4CDW@SOIC16 [CX1033]  
MC68HC908QB4CDW@SOIC16(a trim) [CX1033]  
MC68HC908QB4CDWE@SOIC16 [CX1033]  
MC68HC908QB4CDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB4CP MC68HC908QB4CP(a trim)  
MC68HC908QB4CPE MC68HC908QB4CPE(a trim)  
MC68HC908QB4MDT@TSSOP16 [CX1001]  
MC68HC908QB4MDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB4MDTE@TSSOP16 [CX1001]  
MC68HC908QB4MDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB4MDW@SOIC16 [CX1033]  
MC68HC908QB4MDW@SOIC16(a trim) [CX1033]  
MC68HC908QB4MDWE@SOIC16 [CX1033]  
MC68HC908QB4MDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB4MP MC68HC908QB4MP(a trim)  
MC68HC908QB4MPE MC68HC908QB4MPE(a trim)  
MC68HC908QB4VDT@TSSOP16 [CX1001]  
MC68HC908QB4VDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB4VDTE@TSSOP16 [CX1001]  
MC68HC908QB4VDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB4VDW@SOIC16 [CX1033]  
MC68HC908QB4VDW@SOIC16(a trim) [CX1033]  
MC68HC908QB4VDWE@SOIC16 [CX1033]  
MC68HC908QB4VDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB4VP MC68HC908QB4VP(a trim)  
MC68HC908QB4VPE MC68HC908QB4VPE(a trim)  
MC68HC908QB8CDT@TSSOP16 [CX1001]  
MC68HC908QB8CDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB8CDTE@TSSOP16 [CX1001]  
MC68HC908QB8CDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB8CDW@SOIC16 [CX1033]  
MC68HC908QB8CDW@SOIC16(a trim) [CX1033]  
MC68HC908QB8CDWE@SOIC16 [CX1033]  
MC68HC908QB8CDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB8CP MC68HC908QB8CP(a trim)  
MC68HC908QB8CPE MC68HC908QB8CPE(a trim)  
MC68HC908QB8MDT@TSSOP16 [CX1001]  
MC68HC908QB8MDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB8MDTE@TSSOP16 [CX1001]  
MC68HC908QB8MDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB8MDW@SOIC16 [CX1033]  
MC68HC908QB8MDW@SOIC16(a trim) [CX1033]  
MC68HC908QB8MDWE@SOIC16 [CX1033]  
MC68HC908QB8MDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB8MP MC68HC908QB8MP(a trim)  
MC68HC908QB8MPE MC68HC908QB8MPE(a trim)  
MC68HC908QB8VDT@TSSOP16 [CX1001]  
MC68HC908QB8VDT@TSSOP16(a trim) [CX1001]  
MC68HC908QB8VDTE@TSSOP16 [CX1001]  
MC68HC908QB8VDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QB8VDW@SOIC16 [CX1033]  
MC68HC908QB8VDW@SOIC16(a trim) [CX1033]  
MC68HC908QB8VDWE@SOIC16 [CX1033]  
MC68HC908QB8VDWE@SOIC16(a trim) [CX1033]  
MC68HC908QB8VP MC68HC908QB8VP(a trim)

MC68HC908QB8VPE  
MC68HC908QC16CDR@TSSOP28 [CX1001]  
MC68HC908QC16CDRE@TSSOP28 [CX1001]  
MC68HC908QC16CDS@TSSOP20 [CX1001]  
MC68HC908QC16CDSE@TSSOP20 [CX1001]  
MC68HC908QC16CDT@TSSOP16 [CX1001]  
MC68HC908QC16CDTE@TSSOP16 [CX1001]  
MC68HC908QC16CDX@SOIC16 [CX1033]  
MC68HC908QC16CDXE@SOIC16 [CX1033]  
MC68HC908QC16CDY@SOIC20 [CX1033]  
MC68HC908QC16CDYE@SOIC20 [CX1033]  
MC68HC908QC16CDZ@SOIC28 [CX1033]  
MC68HC908QC16CDZE@SOIC28 [CX1033]  
MC68HC908QC16MDR@TSSOP28 [CX1001]  
MC68HC908QC16MDRE@TSSOP28 [CX1001]  
MC68HC908QC16MDS@TSSOP20 [CX1001]  
MC68HC908QC16MDSE@TSSOP20 [CX1001]  
MC68HC908QC16MDT@TSSOP16 [CX1001]  
MC68HC908QC16MDTE@TSSOP16 [CX1001]  
MC68HC908QC16MDX@SOIC16 [CX1033]  
MC68HC908QC16MDXE@SOIC16 [CX1033]  
MC68HC908QC16MDY@SOIC20 [CX1033]  
MC68HC908QC16MDYE@SOIC20 [CX1033]  
MC68HC908QC16MDZ@SOIC28 [CX1033]  
MC68HC908QC16MDZE@SOIC28 [CX1033]  
MC68HC908QC16VDR@TSSOP28 [CX1001]  
MC68HC908QC16VDRE@TSSOP28 [CX1001]  
MC68HC908QC16VDS@TSSOP20 [CX1001]  
MC68HC908QC16VDSE@TSSOP20 [CX1001]  
MC68HC908QC16VDT@TSSOP16 [CX1001]  
MC68HC908QC16VDTE@TSSOP16 [CX1001]  
MC68HC908QC16VDX@SOIC16 [CX1033]  
MC68HC908QC16VDXE@SOIC16 [CX1033]  
MC68HC908QC16VDY@SOIC20 [CX1033]  
MC68HC908QC16VDYE@SOIC20 [CX1033]  
MC68HC908QC16VDZ@SOIC28 [CX1033]  
MC68HC908QC16VDZE@SOIC28 [CX1033]  
MC68HC908QC4CDR@TSSOP28 [CX1001]  
MC68HC908QC4CDRE@TSSOP28 [CX1001]  
MC68HC908QC4CDS@TSSOP20 [CX1001]  
MC68HC908QC4CDSE@TSSOP20 [CX1001]  
MC68HC908QC4CDT@TSSOP16 [CX1001]  
MC68HC908QC4CDTE@TSSOP16 [CX1001]  
MC68HC908QC4CDX@SOIC16 [CX1033]  
MC68HC908QC4CDY@SOIC20 [CX1033]  
MC68HC908QC4CDZ@SOIC28 [CX1033]  
MC68HC908QC4MDR@TSSOP28 [CX1001]  
MC68HC908QC4MDRE@TSSOP28 [CX1001]  
MC68HC908QC4MDS@TSSOP20 [CX1001]  
MC68HC908QC4MDSE@TSSOP20 [CX1001]  
MC68HC908QC4MDT@TSSOP16 [CX1001]  
MC68HC908QC4MDTE@TSSOP16 [CX1001]  
MC68HC908QC4MDX@SOIC16 [CX1033]  
MC68HC908QC4MDY@SOIC20 [CX1033]  
MC68HC908QC4MDZ@SOIC28 [CX1033]  
MC68HC908QC4VDR@TSSOP28 [CX1001]  
MC68HC908QC4VDRE@TSSOP28 [CX1001]  
MC68HC908QC4VDS@TSSOP20 [CX1001]  
MC68HC908QC4VDSE@TSSOP20 [CX1001]

MC68HC908QB8VPE(a trim)

MC68HC908QC4CDXE@SOIC16 [CX1033]  
MC68HC908QC4CDYE@SOIC20 [CX1033]  
MC68HC908QC4CDZE@SOIC28 [CX1033]

MC68HC908QC4MDXE@SOIC16 [CX1033]  
MC68HC908QC4MDYE@SOIC20 [CX1033]  
MC68HC908QC4MDZE@SOIC28 [CX1033]

MC68HC908QC4VDT@TSSOP16 [CX1001]  
MC68HC908QC4VDTE@TSSOP16 [CX1001]  
MC68HC908QC4VDX@SOIC16 [CX1033]  
MC68HC908QC4VDY@SOIC20 [CX1033]  
MC68HC908QC4VDZ@SOIC28 [CX1033]  
MC68HC908QC8CDR@TSSOP28 [CX1001]  
MC68HC908QC8CDRE@TSSOP28 [CX1001]  
MC68HC908QC8CDS@TSSOP20 [CX1001]  
MC68HC908QC8CDSE@TSSOP20 [CX1001]  
MC68HC908QC8CDT@TSSOP16 [CX1001]  
MC68HC908QC8CDTE@TSSOP16 [CX1001]  
MC68HC908QC8CDX@SOIC16 [CX1033]  
MC68HC908QC8CDY@SOIC20 [CX1033]  
MC68HC908QC8CDZ@SOIC28 [CX1033]  
MC68HC908QC8MDR@TSSOP28 [CX1001]  
MC68HC908QC8MDRE@TSSOP28 [CX1001]  
MC68HC908QC8MDS@TSSOP20 [CX1001]  
MC68HC908QC8MDSE@TSSOP20 [CX1001]  
MC68HC908QC8MDT@TSSOP16 [CX1001]  
MC68HC908QC8MDTE@TSSOP16 [CX1001]  
MC68HC908QC8MDX@SOIC16 [CX1033]  
MC68HC908QC8MDY@SOIC20 [CX1033]  
MC68HC908QC8MDZ@SOIC28 [CX1033]  
MC68HC908QC8VDR@TSSOP28 [CX1001]  
MC68HC908QC8VDRE@TSSOP28 [CX1001]  
MC68HC908QC8VDS@TSSOP20 [CX1001]  
MC68HC908QC8VDSE@TSSOP20 [CX1001]  
MC68HC908QC8VDT@TSSOP16 [CX1001]  
MC68HC908QC8VDTE@TSSOP16 [CX1001]  
MC68HC908QC8VDX@SOIC16 [CX1033]  
MC68HC908QC8VDY@SOIC20 [CX1033]  
MC68HC908QC8VDZ@SOIC28 [CX1033]  
MC68HC908QF4CFJ@QFP32 [CX3001]  
MC68HC908QF4MFJ@QFP32 [CX3001]  
MC68HC908QF4VFJ@QFP32 [CX3001]  
MC68HC908QL2CDT@TSSOP16 [CX1001]  
MC68HC908QL2CDTE@TSSOP16 [CX1001]  
MC68HC908QL2CDW@SOIC16 [CX1032]  
MC68HC908QL2MDT@TSSOP16 [CX1001]  
MC68HC908QL2MDTE@TSSOP16 [CX1001]  
MC68HC908QL2MDW@SOIC16 [CX1032]  
MC68HC908QL2VDT@TSSOP16 [CX1001]  
MC68HC908QL2VDTE@TSSOP16 [CX1001]  
MC68HC908QL2VDW@SOIC16 [CX1032]  
MC68HC908QL3CDT@TSSOP16 [CX1001]  
MC68HC908QL3CDTE@TSSOP16 [CX1001]  
MC68HC908QL3CDW@SOIC16 [CX1032]  
MC68HC908QL3MDT@TSSOP16 [CX1001]  
MC68HC908QL3MDTE@TSSOP16 [CX1001]  
MC68HC908QL3MDW@SOIC16 [CX1032]  
MC68HC908QL3VDT@TSSOP16 [CX1001]  
MC68HC908QL3VDTE@TSSOP16 [CX1001]  
MC68HC908QL3VDW@SOIC16 [CX1032]  
MC68HC908QL4CDT@TSSOP16 [CX1001]  
MC68HC908QL4CDTE@TSSOP16 [CX1001]  
MC68HC908QL4CDW@SOIC16 [CX1032]  
MC68HC908QL4MDT@TSSOP16 [CX1001]  
MC68HC908QL4MDTE@TSSOP16 [CX1001]  
MC68HC908QL4MDW@SOIC16 [CX1032]  
MC68HC908QC4VDXE@SOIC16 [CX1033]  
MC68HC908QC4VDYE@SOIC20 [CX1033]  
MC68HC908QC4VDZE@SOIC28 [CX1033]  
MC68HC908QC8CDXE@SOIC16 [CX1033]  
MC68HC908QC8CDYE@SOIC20 [CX1033]  
MC68HC908QC8CDZE@SOIC28 [CX1033]  
MC68HC908QC8MDXE@SOIC16 [CX1033]  
MC68HC908QC8MDYE@SOIC20 [CX1033]  
MC68HC908QC8MDZE@SOIC28 [CX1033]  
MC68HC908QC8VDXE@SOIC16 [CX1033]  
MC68HC908QC8VDYE@SOIC20 [CX1033]  
MC68HC908QC8VDZE@SOIC28 [CX1033]  
MC68HC908QF4CFJE@QFP32 [CX3001]  
MC68HC908QF4MFJE@QFP32 [CX3001]  
MC68HC908QF4VFJE@QFP32 [CX3001]  
MC68HC908QL2CDWE@SOIC16 [CX1032]  
MC68HC908QL2MDWE@SOIC16 [CX1032]  
MC68HC908QL2VDWE@SOIC16 [CX1032]  
MC68HC908QL3CDWE@SOIC16 [CX1032]  
MC68HC908QL3MDWE@SOIC16 [CX1032]  
MC68HC908QL3VDWE@SOIC16 [CX1032]  
MC68HC908QL4CDWE@SOIC16 [CX1032]  
MC68HC908QL4MDWE@SOIC16 [CX1032]

MC68HC908QL4VDT@TSSOP16 [CX1001]  
MC68HC908QL4VDTE@TSSOP16 [CX1001]  
MC68HC908QL4VDW@SOIC16 [CX1032] MC68HC908QL4VDWE@SOIC16 [CX1032]  
MC68HC908QT1ACDW@SOIC8 [CX1032]  
MC68HC908QT1ACDW@SOIC8(a trim) [CX1032]  
MC68HC908QT1ACDWE@SOIC8 [CX1032]  
MC68HC908QT1ACDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT1ACFQ@DFN8 [CX4004]  
MC68HC908QT1ACFQ@DFN8(a trim) [CX4004]  
MC68HC908QT1ACFQE@DFN8 [CX4004]  
MC68HC908QT1ACFQE@DFN8(a trim) [CX4004]  
MC68HC908QT1ACP MC68HC908QT1ACP(a trim)  
MC68HC908QT1ACPE MC68HC908QT1ACPE(a trim)  
MC68HC908QT1AMDW@SOIC8 [CX1032]  
MC68HC908QT1AMDW@SOIC8(a trim) [CX1032]  
MC68HC908QT1AMDWE@SOIC8 [CX1032]  
MC68HC908QT1AMDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT1AMFQ@DFN8 [CX4004]  
MC68HC908QT1AMFQ@DFN8(a trim) [CX4004]  
MC68HC908QT1AMFQE@DFN8 [CX4004]  
MC68HC908QT1AMFQE@DFN8(a trim) [CX4004]  
MC68HC908QT1AMP MC68HC908QT1AMP(a trim)  
MC68HC908QT1AMPE MC68HC908QT1AMPE(a trim)  
MC68HC908QT1AVDW@SOIC8 [CX1032]  
MC68HC908QT1AVDW@SOIC8(a trim) [CX1032]  
MC68HC908QT1AVDWE@SOIC8 [CX1032]  
MC68HC908QT1AVDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT1AVFQ@DFN8 [CX4004]  
MC68HC908QT1AVFQ@DFN8(a trim) [CX4004]  
MC68HC908QT1AVFQE@DFN8 [CX4004]  
MC68HC908QT1AVFQE@DFN8(a trim) [CX4004]  
MC68HC908QT1AVP MC68HC908QT1AVP(a trim)  
MC68HC908QT1AVPE MC68HC908QT1AVPE(a trim)  
MC68HC908QT1CDW@SOIC8 [CX1032] MC68HC908QT1CDWE@SOIC8 [CX1032]  
MC68HC908QT1CFQ@DFN8 [CX4004] MC68HC908QT1CFQE@DFN8 [CX4004]  
MC68HC908QT1CP MC68HC908QT1CPE  
MC68HC908QT1MDW@SOIC8 [CX1032] MC68HC908QT1MDWE@SOIC8 [CX1032]  
MC68HC908QT1MFQ@DFN8 [CX4004] MC68HC908QT1MFQE@DFN8 [CX4004]  
MC68HC908QT1MP MC68HC908QT1MPPE  
MC68HC908QT1VDW@SOIC8 [CX1032] MC68HC908QT1VDWE@SOIC8 [CX1032]  
MC68HC908QT1VFQ@DFN8 [CX4004] MC68HC908QT1VFQE@DFN8 [CX4004]  
MC68HC908QT1VP MC68HC908QT1VPE  
MC68HC908QT2ACDW@SOIC8 [CX1032]  
MC68HC908QT2ACDW@SOIC8(a trim) [CX1032]  
MC68HC908QT2ACDWE@SOIC8 [CX1032]  
MC68HC908QT2ACDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT2ACFQ@DFN8 [CX4004]  
MC68HC908QT2ACFQ@DFN8(a trim) [CX4004]  
MC68HC908QT2ACFQE@DFN8 [CX4004]  
MC68HC908QT2ACFQE@DFN8(a trim) [CX4004]  
MC68HC908QT2ACP MC68HC908QT2ACP(a trim)  
MC68HC908QT2ACPE MC68HC908QT2ACPE(a trim)  
MC68HC908QT2AMDW@SOIC8 [CX1032]  
MC68HC908QT2AMDW@SOIC8(a trim) [CX1032]  
MC68HC908QT2AMDWE@SOIC8 [CX1032]  
MC68HC908QT2AMDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT2AMFQ@DFN8 [CX4004]  
MC68HC908QT2AMFQ@DFN8(a trim) [CX4004]  
MC68HC908QT2AMFQE@DFN8 [CX4004]

MC68HC908QT2AMFQE@DFN8(a trim) [CX4004]  
MC68HC908QT2AMP MC68HC908QT2AMP(a trim)  
MC68HC908QT2AMPE MC68HC908QT2AMPE(a trim)  
MC68HC908QT2AVDW@SOIC8 [CX1032]  
MC68HC908QT2AVDW@SOIC8(a trim) [CX1032]  
MC68HC908QT2AVDWE@SOIC8 [CX1032]  
MC68HC908QT2AVDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT2AVFQ@DFN8 [CX4004]  
MC68HC908QT2AVFQ@DFN8(a trim) [CX4004]  
MC68HC908QT2AVFQE@DFN8 [CX4004]  
MC68HC908QT2AVFQE@DFN8(a trim) [CX4004]  
MC68HC908QT2AVP MC68HC908QT2AVP(a trim)  
MC68HC908QT2AVPE MC68HC908QT2AVPE(a trim)  
MC68HC908QT2CDW@SOIC8 [CX1032] MC68HC908QT2CDWE@SOIC8 [CX1032]  
MC68HC908QT2CFQ@DFN8 [CX4004] MC68HC908QT2CFQE@DFN8 [CX4004]  
MC68HC908QT2CP MC68HC908QT2CPE  
MC68HC908QT2MDW@SOIC8 [CX1032] MC68HC908QT2MDWE@SOIC8 [CX1032]  
MC68HC908QT2MFQ@DFN8 [CX4004] MC68HC908QT2MFQE@DFN8 [CX4004]  
MC68HC908QT2MP MC68HC908QT2MPE  
MC68HC908QT2VDW@SOIC8 [CX1032] MC68HC908QT2VDWE@SOIC8 [CX1032]  
MC68HC908QT2VFQ@DFN8 [CX4004] MC68HC908QT2VFQE@DFN8 [CX4004]  
MC68HC908QT2VP MC68HC908QT2VPE  
MC68HC908QT4ACDW@SOIC8 [CX1032]  
MC68HC908QT4ACDW@SOIC8(a trim) [CX1032]  
MC68HC908QT4ACDWE@SOIC8 [CX1032]  
MC68HC908QT4ACDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT4ACFQ@DFN8 [CX4004]  
MC68HC908QT4ACFQ@DFN8(a trim) [CX4004]  
MC68HC908QT4ACFQE@DFN8 [CX4004]  
MC68HC908QT4ACFQE@DFN8(a trim) [CX4004]  
MC68HC908QT4ACP MC68HC908QT4ACP(a trim)  
MC68HC908QT4ACPE MC68HC908QT4ACPE(a trim)  
MC68HC908QT4AMDW@SOIC8 [CX1032]  
MC68HC908QT4AMDW@SOIC8(a trim) [CX1032]  
MC68HC908QT4AMDWE@SOIC8 [CX1032]  
MC68HC908QT4AMDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT4AMFQ@DFN8 [CX4004]  
MC68HC908QT4AMFQ@DFN8(a trim) [CX4004]  
MC68HC908QT4AMFQE@DFN8 [CX4004]  
MC68HC908QT4AMFQE@DFN8(a trim) [CX4004]  
MC68HC908QT4AMP MC68HC908QT4AMP(a trim)  
MC68HC908QT4AMPE MC68HC908QT4AMPE(a trim)  
MC68HC908QT4AVDW@SOIC8 [CX1032]  
MC68HC908QT4AVDW@SOIC8(a trim) [CX1032]  
MC68HC908QT4AVDWE@SOIC8 [CX1032]  
MC68HC908QT4AVDWE@SOIC8(a trim) [CX1032]  
MC68HC908QT4AVFQ@DFN8 [CX4004]  
MC68HC908QT4AVFQ@DFN8(a trim) [CX4004]  
MC68HC908QT4AVFQE@DFN8 [CX4004]  
MC68HC908QT4AVFQE@DFN8(a trim) [CX4004]  
MC68HC908QT4AVP MC68HC908QT4AVP(a trim)  
MC68HC908QT4AVPE MC68HC908QT4AVPE(a trim)  
MC68HC908QT4CDW@SOIC8 [CX1032] MC68HC908QT4CDWE@SOIC8 [CX1032]  
MC68HC908QT4CFQ@DFN8 [CX4004] MC68HC908QT4CFQE@DFN8 [CX4004]  
MC68HC908QT4CP MC68HC908QT4CPE  
MC68HC908QT4MDW@SOIC8 [CX1032] MC68HC908QT4MDWE@SOIC8 [CX1032]  
MC68HC908QT4MFQ@DFN8 [CX4004] MC68HC908QT4MFQE@DFN8 [CX4004]  
MC68HC908QT4MP MC68HC908QT4MPE  
MC68HC908QT4VDW@SOIC8 [CX1032] MC68HC908QT4VDWE@SOIC8 [CX1032]

MC68HC908QT4VFQ@DFN8 [CX4004]                   MC68HC908QT4VFE@DFN8 [CX4004]  
MC68HC908QT4VP                                   MC68HC908QT4VPE  
MC68HC908QY1ACDT@TSSOP16 [CX1001]  
MC68HC908QY1ACDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY1ACDTE@TSSOP16 [CX1001]  
MC68HC908QY1ACDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY1ACDW@SOIC16 [CX1033]  
MC68HC908QY1ACDW@SOIC16(a trim) [CX1033]  
MC68HC908QY1ACDWE@SOIC16 [CX1033]  
MC68HC908QY1ACDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY1ACP                               MC68HC908QY1ACP(a trim)  
MC68HC908QY1ACPE                              MC68HC908QY1ACPE(a trim)  
MC68HC908QY1AMDT@TSSOP16 [CX1001]  
MC68HC908QY1AMDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AMDTE@TSSOP16 [CX1001]  
MC68HC908QY1AMDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AMDW@SOIC16 [CX1033]  
MC68HC908QY1AMDW@SOIC16(a trim) [CX1033]  
MC68HC908QY1AMDWE@SOIC16 [CX1033]  
MC68HC908QY1AMDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY1AMP                              MC68HC908QY1AMP(a trim)  
MC68HC908QY1AMPE                             MC68HC908QY1AMPE(a trim)  
MC68HC908QY1AVDT@TSSOP16 [CX1001]  
MC68HC908QY1AVDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AVDTE@TSSOP16 [CX1001]  
MC68HC908QY1AVDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY1AVDW@SOIC16 [CX1033]  
MC68HC908QY1AVDW@SOIC16(a trim) [CX1033]  
MC68HC908QY1AVDWE@SOIC16 [CX1033]  
MC68HC908QY1AVDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY1AVP                              MC68HC908QY1AVP(a trim)  
MC68HC908QY1AVPE                             MC68HC908QY1AVPE(a trim)  
MC68HC908QY1CDT@TSSOP16 [CX1001]  
MC68HC908QY1CDTE@TSSOP16 [CX1001]  
MC68HC908QY1CDW@SOIC16 [CX1033]           MC68HC908QY1CDWE@SOIC16 [CX1033]  
MC68HC908QY1CP                               MC68HC908QY1CPE  
MC68HC908QY1MDT@TSSOP16 [CX1001]  
MC68HC908QY1MDTE@TSSOP16 [CX1001]  
MC68HC908QY1MDW@SOIC16 [CX1033]           MC68HC908QY1MDWE@SOIC16 [CX1033]  
MC68HC908QY1MP                               MC68HC908QY1MPE  
MC68HC908QY1VDT@TSSOP16 [CX1001]  
MC68HC908QY1VDTE@TSSOP16 [CX1001]  
MC68HC908QY1VDW@SOIC16 [CX1033]           MC68HC908QY1VDWE@SOIC16 [CX1033]  
MC68HC908QY1VP                               MC68HC908QY1VPE  
MC68HC908QY2ACDT@TSSOP16 [CX1001]  
MC68HC908QY2ACDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY2ACDTE@TSSOP16 [CX1001]  
MC68HC908QY2ACDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY2ACDW@SOIC16 [CX1033]  
MC68HC908QY2ACDW@SOIC16(a trim) [CX1033]  
MC68HC908QY2ACDWE@SOIC16 [CX1033]  
MC68HC908QY2ACDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY2ACP                              MC68HC908QY2ACP(a trim)  
MC68HC908QY2ACPE                             MC68HC908QY2ACPE(a trim)  
MC68HC908QY2AMDT@TSSOP16 [CX1001]  
MC68HC908QY2AMDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY2AMDTE@TSSOP16 [CX1001]  
MC68HC908QY2AMDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY2AMDW@SOIC16 [CX1033]

MC68HC908QY2AMDW@SOIC16(a trim) [CX1033]  
MC68HC908QY2AMDWE@SOIC16 [CX1033]  
MC68HC908QY2AMDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY2AMP MC68HC908QY2AMP(a trim)  
MC68HC908QY2AMPE MC68HC908QY2AMPE(a trim)  
MC68HC908QY2AVDT@TSSOP16 [CX1001]  
MC68HC908QY2AVDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY2AVDTE@TSSOP16 [CX1001]  
MC68HC908QY2AVDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY2AVDW@SOIC16 [CX1033]  
MC68HC908QY2AVDW@SOIC16(a trim) [CX1033]  
MC68HC908QY2AVDWE@SOIC16 [CX1033]  
MC68HC908QY2AVDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY2AVP MC68HC908QY2AVP(a trim)  
MC68HC908QY2AVPE MC68HC908QY2AVPE(a trim)  
MC68HC908QY2CDT@TSSOP16 [CX1001]  
MC68HC908QY2CDTE@TSSOP16 [CX1001]  
MC68HC908QY2CDW@SOIC16 [CX1033] MC68HC908QY2CDWE@SOIC16 [CX1033]  
MC68HC908QY2CP MC68HC908QY2CPE  
MC68HC908QY2MDT@TSSOP16 [CX1001]  
MC68HC908QY2MDTE@TSSOP16 [CX1001]  
MC68HC908QY2MDW@SOIC16 [CX1033] MC68HC908QY2MDWE@SOIC16 [CX1033]  
MC68HC908QY2MP MC68HC908QY2MPE  
MC68HC908QY2VDT@TSSOP16 [CX1001]  
MC68HC908QY2VDTE@TSSOP16 [CX1001]  
MC68HC908QY2VDW@SOIC16 [CX1033] MC68HC908QY2VDWE@SOIC16 [CX1033]  
MC68HC908QY2VP MC68HC908QY2VPE  
MC68HC908QY4ACDT@TSSOP16 [CX1001]  
MC68HC908QY4ACDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY4ACDTE@TSSOP16 [CX1001]  
MC68HC908QY4ACDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY4ACDW@SOIC16 [CX1033]  
MC68HC908QY4ACDW@SOIC16(a trim) [CX1033]  
MC68HC908QY4ACDWE@SOIC16 [CX1033]  
MC68HC908QY4ACDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY4ACP MC68HC908QY4ACP(a trim)  
MC68HC908QY4ACPE MC68HC908QY4ACPE(a trim)  
MC68HC908QY4AMDT@TSSOP16 [CX1001]  
MC68HC908QY4AMDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AMDTE@TSSOP16 [CX1001]  
MC68HC908QY4AMDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AMDW@SOIC16 [CX1033]  
MC68HC908QY4AMDW@SOIC16(a trim) [CX1033]  
MC68HC908QY4AMDWE@SOIC16 [CX1033]  
MC68HC908QY4AMDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY4AMP MC68HC908QY4AMP(a trim)  
MC68HC908QY4AMPE MC68HC908QY4AMPE(a trim)  
MC68HC908QY4AVDT@TSSOP16 [CX1001]  
MC68HC908QY4AVDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AVDTE@TSSOP16 [CX1001]  
MC68HC908QY4AVDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY4AVDW@SOIC16 [CX1033]  
MC68HC908QY4AVDW@SOIC16(a trim) [CX1033]  
MC68HC908QY4AVDWE@SOIC16 [CX1033]  
MC68HC908QY4AVDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY4AVP MC68HC908QY4AVP(a trim)  
MC68HC908QY4AVPE MC68HC908QY4AVPE(a trim)  
MC68HC908QY4CDT@TSSOP16 [CX1001]  
MC68HC908QY4CDTE@TSSOP16 [CX1001]

MC68HC908QY4CDW@SOIC16 [CX1033]      MC68HC908QY4CDWE@SOIC16 [CX1033]  
MC68HC908QY4CP      MC68HC908QY4CPE  
MC68HC908QY4MDT@TSSOP16 [CX1001]  
MC68HC908QY4MDTE@TSSOP16 [CX1001]  
MC68HC908QY4MDW@SOIC16 [CX1033]      MC68HC908QY4MDWE@SOIC16 [CX1033]  
MC68HC908QY4MP      MC68HC908QY4MPPE  
MC68HC908QY4VDT@TSSOP16 [CX1001]  
MC68HC908QY4VDTE@TSSOP16 [CX1001]  
MC68HC908QY4VDW@SOIC16 [CX1033]      MC68HC908QY4VDWE@SOIC16 [CX1033]  
MC68HC908QY4VP      MC68HC908QY4VPE  
MC68HC908QY8CDT@TSSOP16 [CX1001]  
MC68HC908QY8CDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY8CDTE@TSSOP16 [CX1001]  
MC68HC908QY8CDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY8CDW@SOIC16 [CX1033]  
MC68HC908QY8CDW@SOIC16(a trim) [CX1033]  
MC68HC908QY8CDWE@SOIC16 [CX1033]  
MC68HC908QY8CDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY8CP      MC68HC908QY8CP(a trim)  
MC68HC908QY8CPE      MC68HC908QY8CPE(a trim)  
MC68HC908QY8MDT@TSSOP16 [CX1001]  
MC68HC908QY8MDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY8MDTE@TSSOP16 [CX1001]  
MC68HC908QY8MDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY8MDW@SOIC16 [CX1033]  
MC68HC908QY8MDW@SOIC16(a trim) [CX1033]  
MC68HC908QY8MDWE@SOIC16 [CX1033]  
MC68HC908QY8MDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY8MP      MC68HC908QY8MP(a trim)  
MC68HC908QY8MPPE      MC68HC908QY8MPPE(a trim)  
MC68HC908QY8VDT@TSSOP16 [CX1001]  
MC68HC908QY8VDT@TSSOP16(a trim) [CX1001]  
MC68HC908QY8VDTE@TSSOP16 [CX1001]  
MC68HC908QY8VDTE@TSSOP16(a trim) [CX1001]  
MC68HC908QY8VDW@SOIC16 [CX1033]  
MC68HC908QY8VDW@SOIC16(a trim) [CX1033]  
MC68HC908QY8VDWE@SOIC16 [CX1033]  
MC68HC908QY8VDWE@SOIC16(a trim) [CX1033]  
MC68HC908QY8VP      MC68HC908QY8VP(a trim)  
MC68HC908QY8VPE      MC68HC908QY8VPE(a trim)  
MC68HC908SR12CB@SDIP42 [CX0042]      MC68HC908SR12CBE@SDIP42 [CX0042]  
MC68HC908SR12CFA@TQFP48 [CX3007]  
MC68HC908SR12CFAE@TQFP48 [CX3007]  
MC68HC908SR12MB@SDIP42 [CX0042]      MC68HC908SR12MBE@SDIP42 [CX0042]  
MC68HC908SR12MFA@TQFP48 [CX3007]  
MC68HC908SR12MFAE@TQFP48 [CX3007]  
MC68HC908SR12VB@SDIP42 [CX0042]      MC68HC908SR12VBE@SDIP42 [CX0042]  
MC68HC908SR12VFA@TQFP48 [CX3007]  
MC68HC908SR12VFAE@TQFP48 [CX3007]  
MC68HCP11E1@PLCC52 [CX2052]      MC68HCP11E1@QFP52 [CX3010]  
MC68HCP11E1CFU2 [CX3044]      MC68HCP11E1CFU3 [CX3044]  
MC68HCP11E1MFU2 [CX3044]      MC68HCP11E1VFU2 [CX3044]  
MC68HLC908JK1EIDW@SOIC20 [CX1033]  
MC68HLC908JK1EIDWE@SOIC20 [CX1033]  
MC68HLC908JK1EIP      MC68HLC908JK1EIPPE  
MC68HLC908JK3EIDW@SOIC20 [CX1033]  
MC68HLC908JK3EIDWE@SOIC20 [CX1033]  
MC68HLC908JK3EIP      MC68HLC908JK3EIPPE  
MC68HLC908JL3EIDW@SOIC28 [CX1033]



MC68HLC908JL3EIDWE@SOIC28 [CX1033]  
MC68HLC908JL3EIFA@TQFP48 [CX3007]  
MC68HLC908JL3EIFAE@TQFP48 [CX3007]  
MC68HLC908JL3EIP MC68HLC908JL3EIP  
MC68HRC908JK1CDW@SOIC20 [CX1033]  
MC68HRC908JK1CDWE@SOIC20 [CX1033]  
MC68HRC908JK1CP MC68HRC908JK1CPE  
MC68HRC908JK1ECDW@SOIC20 [CX1033]  
MC68HRC908JK1ECDWE@SOIC20 [CX1033]  
MC68HRC908JK1ECP MC68HRC908JK1ECPE  
MC68HRC908JK1EMDW@SOIC20 [CX1033]  
MC68HRC908JK1EMDWE@SOIC20 [CX1033]  
MC68HRC908JK1EMP MC68HRC908JK1EMPE  
MC68HRC908JK1EVDW@SOIC20 [CX1033]  
MC68HRC908JK1EVDWE@SOIC20 [CX1033]  
MC68HRC908JK1EVP MC68HRC908JK1EVPE  
MC68HRC908JK1MDW@SOIC20 [CX1033]  
MC68HRC908JK1MDWE@SOIC20 [CX1033]  
MC68HRC908JK1MP MC68HRC908JK1MPE  
MC68HRC908JK1VDW@SOIC20 [CX1033]  
MC68HRC908JK1VDWE@SOIC20 [CX1033]  
MC68HRC908JK1VP MC68HRC908JK1VPE  
MC68HRC908JK3CDW@SOIC20 [CX1033]  
MC68HRC908JK3CDWE@SOIC20 [CX1033]  
MC68HRC908JK3CP MC68HRC908JK3CPE  
MC68HRC908JK3ECDW@SOIC20 [CX1033]  
MC68HRC908JK3ECDWE@SOIC20 [CX1033]  
MC68HRC908JK3ECP MC68HRC908JK3ECPE  
MC68HRC908JK3EMDW@SOIC20 [CX1033]  
MC68HRC908JK3EMDWE@SOIC20 [CX1033]  
MC68HRC908JK3EMP MC68HRC908JK3EMPE  
MC68HRC908JK3EVDW@SOIC20 [CX1033]  
MC68HRC908JK3EVDWE@SOIC20 [CX1033]  
MC68HRC908JK3EVP MC68HRC908JK3EVPE  
MC68HRC908JK3MDW@SOIC20 [CX1033]  
MC68HRC908JK3MDWE@SOIC20 [CX1033]  
MC68HRC908JK3MP MC68HRC908JK3MPE  
MC68HRC908JK3VDW@SOIC20 [CX1033]  
MC68HRC908JK3VDWE@SOIC20 [CX1033]  
MC68HRC908JK3VP MC68HRC908JK3VPE  
MC68HRC908JL3CDW@SOIC28 [CX1033]  
MC68HRC908JL3CDWE@SOIC28 [CX1033]  
MC68HRC908JL3CP MC68HRC908JL3CPE  
MC68HRC908JL3ECDW@SOIC28 [CX1033]  
MC68HRC908JL3ECDWE@SOIC28 [CX1033]  
MC68HRC908JL3ECFA@TQFP48 [CX3007]  
MC68HRC908JL3ECFAE@TQFP48 [CX3007]  
MC68HRC908JL3ECP MC68HRC908JL3ECPE  
MC68HRC908JL3EMDW@SOIC28 [CX1033]  
MC68HRC908JL3EMDWE@SOIC28 [CX1033]  
MC68HRC908JL3EMFA@TQFP48 [CX3007]  
MC68HRC908JL3EMFAE@TQFP48 [CX3007]  
MC68HRC908JL3EMP MC68HRC908JL3EMPE  
MC68HRC908JL3EVDW@SOIC28 [CX1033]  
MC68HRC908JL3EVDWE@SOIC28 [CX1033]  
MC68HRC908JL3EVFA@TQFP48 [CX3007]  
MC68HRC908JL3EVFAE@TQFP48 [CX3007]  
MC68HRC908JL3EVP MC68HRC908JL3EVPE  
MC68HRC908JL3MDW@SOIC28 [CX1033]

MC68HRC908JL3MDWE@SOIC28 [CX1033]  
MC68HRC908JL3MP MC68HRC908JL3MPE  
MC68HRC908JL3VDW@SOIC28 [CX1033]  
MC68HRC908JL3VDWE@SOIC28 [CX1033]  
MC68HRC908JL3VP MC68HRC908JL3VPE  
MC68HSC705C8A [CX0001] MC68HSC705C8A@PLCC44 [CX2044]  
MC68HSC705C8A@SDIP42 [CX0042] MC68HSC705C8A@TQFP44 [CX3002]  
MC68S711E9@PLCC52 [CX2052] MC68S711E9FN@PLCC52 [CX2052]  
MC9RS08KA1CDB@DFN6 [CX4000]  
MC9RS08KA1CDB@DFN6(auto trim) [CX4000]  
MC9RS08KA1CDBE@DFN6 [CX4000]  
MC9RS08KA1CDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA1CPC MC9RS08KA1CPC(auto trim)  
MC9RS08KA1CPCE MC9RS08KA1CPCE(auto trim)  
MC9RS08KA1CSC@SOIC8 [CX1030]  
MC9RS08KA1CSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA1CSCE@SOIC8 [CX1030]  
MC9RS08KA1CSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA1MDB@DFN6 [CX4000]  
MC9RS08KA1MDB@DFN6(auto trim) [CX4000]  
MC9RS08KA1MDBE@DFN6 [CX4000]  
MC9RS08KA1MDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA1MPC MC9RS08KA1MPC(auto trim)  
MC9RS08KA1MPCE MC9RS08KA1MPCE(auto trim)  
MC9RS08KA1MSC@SOIC8 [CX1030]  
MC9RS08KA1MSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA1MSCE@SOIC8 [CX1030]  
MC9RS08KA1MSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA1VDB@DFN6 [CX4000]  
MC9RS08KA1VDB@DFN6(auto trim) [CX4000]  
MC9RS08KA1VDBE@DFN6 [CX4000]  
MC9RS08KA1VDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA1VPC MC9RS08KA1VPC(auto trim)  
MC9RS08KA1VPCE MC9RS08KA1VPCE(auto trim)  
MC9RS08KA1VSC@SOIC8 [CX1030]  
MC9RS08KA1VSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA1VSCE@SOIC8 [CX1030]  
MC9RS08KA1VSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA2CDB@DFN6 [CX4000]  
MC9RS08KA2CDB@DFN6(auto trim) [CX4000]  
MC9RS08KA2CDBE@DFN6 [CX4000]  
MC9RS08KA2CDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA2CPC MC9RS08KA2CPC(auto trim)  
MC9RS08KA2CPCE MC9RS08KA2CPCE(auto trim)  
MC9RS08KA2CSC@SOIC8 [CX1030]  
MC9RS08KA2CSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA2CSCE@SOIC8 [CX1030]  
MC9RS08KA2CSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA2MDB@DFN6 [CX4000]  
MC9RS08KA2MDB@DFN6(auto trim) [CX4000]  
MC9RS08KA2MDBE@DFN6 [CX4000]  
MC9RS08KA2MDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA2MPC MC9RS08KA2MPC(auto trim)  
MC9RS08KA2MPCE MC9RS08KA2MPCE(auto trim)  
MC9RS08KA2MSC@SOIC8 [CX1030]  
MC9RS08KA2MSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA2MSCE@SOIC8 [CX1030]  
MC9RS08KA2MSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA2VDB@DFN6 [CX4000]

MC9RS08KA2VDB@DFN6(auto trim) [CX4000]  
MC9RS08KA2VDBE@DFN6 [CX4000]  
MC9RS08KA2VDBE@DFN6(auto trim) [CX4000]  
MC9RS08KA2VPC MC9RS08KA2VPC(auto trim)  
MC9RS08KA2VPCE MC9RS08KA2VPCE(auto trim)  
MC9RS08KA2VSC@SOIC8 [CX1030]  
MC9RS08KA2VSC@SOIC8(auto trim) [CX1030]  
MC9RS08KA2VSCE@SOIC8 [CX1030]  
MC9RS08KA2VSCE@SOIC8(auto trim) [CX1030]  
MC9RS08KA4CPG MC9RS08KA4CPG(auto trim)  
MC9RS08KA4CPGE MC9RS08KA4CPGE(auto trim)  
MC9RS08KA4CPJ MC9RS08KA4CPJ(auto trim)  
MC9RS08KA4CPJE MC9RS08KA4CPJE(auto trim)  
MC9RS08KA4CTG@TSSOP16 [CX1001]  
MC9RS08KA4CTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4CTGE@TSSOP16 [CX1001]  
MC9RS08KA4CTGE@TSSOP16(a trim) [CX1001]  
MC9RS08KA4CWG@SOIC16 [CX1033]  
MC9RS08KA4CWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA4CWGE@SOIC16 [CX1033]  
MC9RS08KA4CWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA4CWJ@SOIC20 [CX1033]  
MC9RS08KA4CWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA4CWJE@SOIC20 [CX1033]  
MC9RS08KA4CWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA4MPG MC9RS08KA4MPG(auto trim)  
MC9RS08KA4MPGE MC9RS08KA4MPGE(auto trim)  
MC9RS08KA4MPJ MC9RS08KA4MPJ(auto trim)  
MC9RS08KA4MPJE MC9RS08KA4MPJE(auto trim)  
MC9RS08KA4MTG@TSSOP16 [CX1001]  
MC9RS08KA4MTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4MTGE@TSSOP16 [CX1001]  
MC9RS08KA4MTGE@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4MWG@SOIC16 [CX1033]  
MC9RS08KA4MWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA4MWGE@SOIC16 [CX1033]  
MC9RS08KA4MWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA4MWJ@SOIC20 [CX1033]  
MC9RS08KA4MWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA4MWJE@SOIC20 [CX1033]  
MC9RS08KA4MWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA4VPG MC9RS08KA4VPG(auto trim)  
MC9RS08KA4VPGE MC9RS08KA4VPGE(auto trim)  
MC9RS08KA4VPJ MC9RS08KA4VPJ(auto trim)  
MC9RS08KA4VPJE MC9RS08KA4VPJE(auto trim)  
MC9RS08KA4VTG@TSSOP16 [CX1001]  
MC9RS08KA4VTG@TSSOP16(auto trim) [CX1001]  
MC9RS08KA4VTGE@TSSOP16 [CX1001]  
MC9RS08KA4VTGE@TSSOP16(a trim) [CX1001]  
MC9RS08KA4VWG@SOIC16 [CX1033]  
MC9RS08KA4VWG@SOIC16(auto trim) [CX1033]  
MC9RS08KA4VWGE@SOIC16 [CX1033]  
MC9RS08KA4VWGE@SOIC16(auto trim) [CX1033]  
MC9RS08KA4VWJ@SOIC20 [CX1033]  
MC9RS08KA4VWJ@SOIC20(auto trim) [CX1033]  
MC9RS08KA4VWJE@SOIC20 [CX1033]  
MC9RS08KA4VWJE@SOIC20(auto trim) [CX1033]  
MC9RS08KA8CPG MC9RS08KA8CPG(auto trim)  
MC9RS08KA8CPGE MC9RS08KA8CPGE(auto trim)

MC9RS08KA8CPJ	MC9RS08KA8CPJ(auto trim)
MC9RS08KA8CPJE	MC9RS08KA8CPJE(auto trim)
MC9RS08KA8CTG@TSSOP16 [CX1001]	
MC9RS08KA8CTG@TSSOP16(auto trim) [CX1001]	
MC9RS08KA8CTGE@TSSOP16 [CX1001]	
MC9RS08KA8CTGE@TSSOP16(a trim) [CX1001]	
MC9RS08KA8CWG@SOIC16 [CX1033]	
MC9RS08KA8CWG@SOIC16(auto trim) [CX1033]	
MC9RS08KA8CWGE@SOIC16 [CX1033]	
MC9RS08KA8CWGE@SOIC16(auto trim) [CX1033]	
MC9RS08KA8CWJ@SOIC20 [CX1033]	
MC9RS08KA8CWJ@SOIC20(auto trim) [CX1033]	
MC9RS08KA8CWJE@SOIC20 [CX1033]	
MC9RS08KA8CWJE@SOIC20(auto trim) [CX1033]	
MC9RS08KA8MPG	MC9RS08KA8MPG(auto trim)
MC9RS08KA8MPGE	MC9RS08KA8MPGE(auto trim)
MC9RS08KA8MPJ	MC9RS08KA8MPJ(auto trim)
MC9RS08KA8MPJE	MC9RS08KA8MPJE(auto trim)
MC9RS08KA8MTG@TSSOP16 [CX1001]	
MC9RS08KA8MTG@TSSOP16(auto trim) [CX1001]	
MC9RS08KA8MTGE@TSSOP16 [CX1001]	
MC9RS08KA8MTGE@TSSOP16(a trim) [CX1001]	
MC9RS08KA8MWG@SOIC16 [CX1033]	
MC9RS08KA8MWG@SOIC16(auto trim) [CX1033]	
MC9RS08KA8MWGE@SOIC16 [CX1033]	
MC9RS08KA8MWGE@SOIC16(auto trim) [CX1033]	
MC9RS08KA8MWJ@SOIC20 [CX1033]	
MC9RS08KA8MWJ@SOIC20(auto trim) [CX1033]	
MC9RS08KA8MWJE@SOIC20 [CX1033]	
MC9RS08KA8MWJE@SOIC20(auto trim) [CX1033]	
MC9RS08KA8VPG	MC9RS08KA8VPG(auto trim)
MC9RS08KA8VPGE	MC9RS08KA8VPGE(auto trim)
MC9RS08KA8VPJ	MC9RS08KA8VPJ(auto trim)
MC9RS08KA8VPJE	MC9RS08KA8VPJE(auto trim)
MC9RS08KA8VTG@TSSOP16 [CX1001]	
MC9RS08KA8VTG@TSSOP16(auto trim) [CX1001]	
MC9RS08KA8VTGE@TSSOP16 [CX1001]	
MC9RS08KA8VTGE@TSSOP16(a trim) [CX1001]	
MC9RS08KA8VWG@SOIC16 [CX1033]	
MC9RS08KA8VWG@SOIC16(auto trim) [CX1033]	
MC9RS08KA8VWGE@SOIC16 [CX1033]	
MC9RS08KA8VWGE@SOIC16(auto trim) [CX1033]	
MC9RS08KA8VWJ@SOIC20 [CX1033]	
MC9RS08KA8VWJ@SOIC20(auto trim) [CX1033]	
MC9RS08KA8VWJE@SOIC20 [CX1033]	
MC9RS08KA8VWJE@SOIC20(auto trim) [CX1033]	
MC9RS08KB12CDC@DFN8 [CX4004]	MC9RS08KB12CSC@SOIC8 [CX1030]
MC9RS08KB12CSG@SOIC16 [CX1030]	MC9RS08KB12CTG@TSSOP16 [CX1001]
MC9RS08KB12CWJ@SOIC20 [CX1033]	MC9RS08KB12MDC@DFN8 [CX4004]
MC9RS08KB12MSC@SOIC8 [CX1030]	MC9RS08KB12MSG@SOIC16 [CX1030]
MC9RS08KB12MTG@TSSOP16 [CX1001]	MC9RS08KB12MWJ@SOIC20 [CX1033]
MC9RS08KB12VDC@DFN8 [CX4004]	MC9RS08KB12VSC@SOIC8 [CX1030]
MC9RS08KB12VSG@SOIC16 [CX1030]	MC9RS08KB12VTG@TSSOP16 [CX1001]
MC9RS08KB12VWJ@SOIC20 [CX1033]	MC9RS08KB2CDC@DFN8 [CX4004]
MC9RS08KB2CSC@SOIC8 [CX1030]	MC9RS08KB2CSG@SOIC16 [CX1030]
MC9RS08KB2CTG@TSSOP16 [CX1001]	MC9RS08KB2CWJ@SOIC20 [CX1033]
MC9RS08KB2MDC@DFN8 [CX4004]	MC9RS08KB2MSC@SOIC8 [CX1030]
MC9RS08KB2MSG@SOIC16 [CX1030]	MC9RS08KB2MTG@TSSOP16 [CX1001]
MC9RS08KB2MWJ@SOIC20 [CX1033]	MC9RS08KB2VDC@DFN8 [CX4004]

MC9RS08KB2VSC@SOIC8 [CX1030] MC9RS08KB2VSG@SOIC16 [CX1030]  
MC9RS08KB2VTG@TSSOP16 [CX1001] MC9RS08KB2VWJ@SOIC20 [CX1033]  
MC9RS08KB4CDC@DFN8 [CX4004] MC9RS08KB4CSC@SOIC8 [CX1030]  
MC9RS08KB4CSG@SOIC16 [CX1030] MC9RS08KB4CTG@TSSOP16 [CX1001]  
MC9RS08KB4CWJ@SOIC20 [CX1033] MC9RS08KB4MDC@DFN8 [CX4004]  
MC9RS08KB4MSC@SOIC8 [CX1030] MC9RS08KB4MSG@SOIC16 [CX1030]  
MC9RS08KB4MTG@TSSOP16 [CX1001] MC9RS08KB4MWJ@SOIC20 [CX1033]  
MC9RS08KB4VDC@DFN8 [CX4004] MC9RS08KB4VSC@SOIC8 [CX1030]  
MC9RS08KB4VSG@SOIC16 [CX1030] MC9RS08KB4VTG@TSSOP16 [CX1001]  
MC9RS08KB4VWJ@SOIC20 [CX1033] MC9RS08KB8CDC@DFN8 [CX4004]  
MC9RS08KB8CSC@SOIC8 [CX1030] MC9RS08KB8CSG@SOIC16 [CX1030]  
MC9RS08KB8CTG@TSSOP16 [CX1001] MC9RS08KB8CWJ@SOIC20 [CX1033]  
MC9RS08KB8MDC@DFN8 [CX4004] MC9RS08KB8MSC@SOIC8 [CX1030]  
MC9RS08KB8MSG@SOIC16 [CX1030] MC9RS08KB8MTG@TSSOP16 [CX1001]  
MC9RS08KB8MWJ@SOIC20 [CX1033] MC9RS08KB8VDC@DFN8 [CX4004]  
MC9RS08KB8VSC@SOIC8 [CX1030] MC9RS08KB8VSG@SOIC16 [CX1030]  
MC9RS08KB8VTG@TSSOP16 [CX1001] MC9RS08KB8VWJ@SOIC20 [CX1033]  
MC9RS08LA8CFT@QFN48 [CX4021] MC9RS08LA8CFTE@QFN48 [CX4021]  
MC9RS08LA8CLF@QFP48 [CX3007] MC9RS08LA8CLFE@QFP48 [CX3007]  
MC9RS08LA8MFT@QFN48 [CX4021] MC9RS08LA8MFTE@QFN48 [CX4021]  
MC9RS08LA8MLF@QFP48 [CX3007] MC9RS08LA8MLFE@QFP48 [CX3007]  
MC9RS08LA8VFT@QFN48 [CX4021] MC9RS08LA8VFTE@QFN48 [CX4021]  
MC9RS08LA8VLF@QFP48 [CX3007] MC9RS08LA8VLF@QFP48 [CX3007]  
MC9RS08LE4CWL@SOIC28 [CX1033] MC9RS08LE4CWLE@SOIC28 [CX1033]  
MC9RS08LE4MWL@SOIC28 [CX1033] MC9RS08LE4MWLE@SOIC28 [CX1033]  
MC9RS08LE4VWL@SOIC28 [CX1033] MC9RS08LE4VWLE@SOIC28 [CX1033]  
MC9S08AC128CFG@QFP44 [CX3003] MC9S08AC128CFGE@QFP44 [CX3003]  
MC9S08AC128CFU@QFP64 [CX3014] MC9S08AC128CFUE@QFP64 [CX3014]  
MC9S08AC128CLK@QFP80 [CX3017] MC9S08AC128CLKE@QFP80 [CX3017]  
MC9S08AC128MFG@QFP44 [CX3003] MC9S08AC128MFGE@QFP44 [CX3003]  
MC9S08AC128MFU@QFP64 [CX3014] MC9S08AC128MFUE@QFP64 [CX3014]  
MC9S08AC128MLK@QFP80 [CX3017] MC9S08AC128MLKE@QFP80 [CX3017]  
MC9S08AC128VFG@QFP44 [CX3003] MC9S08AC128VFGE@QFP44 [CX3003]  
MC9S08AC128VFU@QFP64 [CX3014] MC9S08AC128VFUE@QFP64 [CX3014]  
MC9S08AC128VLK@QFP80 [CX3017] MC9S08AC128VLKE@QFP80 [CX3017]  
MC9S08AC16CFD [CX4021] MC9S08AC16CFDE [CX4021]  
MC9S08AC16CFG [CX3003]  
MC9S08AC16CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16CFGE [CX3003]  
MC9S08AC16CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16CFJ [CX3001] MC9S08AC16CFJE [CX3001]  
MC9S08AC16MFD [CX4021] MC9S08AC16MFDE [CX4021]  
MC9S08AC16MFG [CX3003]  
MC9S08AC16MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16MFGE [CX3003]  
MC9S08AC16MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16MFJ [CX3001] MC9S08AC16MFJE [CX3001]  
MC9S08AC16VFD [CX4021] MC9S08AC16VFDE [CX4021]  
MC9S08AC16VFG [CX3003]  
MC9S08AC16VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16VFGE [CX3003]  
MC9S08AC16VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC16VFJ [CX3001] MC9S08AC16VFJE [CX3001]  
MC9S08AC32CFD [CX4021] MC9S08AC32CFDE [CX4021]  
MC9S08AC32CFG [CX3003]  
MC9S08AC32CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32CFGE [CX3003]  
MC9S08AC32CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC32CFJ [CX3001] MC9S08AC32CFJE [CX3001]

MC9S08AC32CFU [CX3014]	MC9S08AC32CFUE [CX3014]
MC9S08AC32CPU [CX3011]	MC9S08AC32CPUE [CX3011]
MC9S08AC32MFD [CX4021]	MC9S08AC32MFDE [CX4021]
MC9S08AC32MFG [CX3003]	
MC9S08AC32MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AC32MFGE [CX3003]	
MC9S08AC32MFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AC32MFJ [CX3001]	MC9S08AC32MFJE [CX3001]
MC9S08AC32MFU [CX3014]	MC9S08AC32MFUE [CX3014]
MC9S08AC32MPU [CX3011]	MC9S08AC32MPUE [CX3011]
MC9S08AC32VFD [CX4021]	MC9S08AC32VFDE [CX4021]
MC9S08AC32VFG [CX3003]	
MC9S08AC32VFG@LQFP44(*) [SA245A+B4404]	
MC9S08AC32VFGE [CX3003]	
MC9S08AC32VFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AC32VFJ [CX3001]	MC9S08AC32VFJE [CX3001]
MC9S08AC32VFU [CX3014]	MC9S08AC32VFUE [CX3014]
MC9S08AC32VPU [CX3011]	MC9S08AC32VPUE [CX3011]
MC9S08AC48CFD [CX4021]	MC9S08AC48CFDE [CX4021]
MC9S08AC48CFG [CX3003]	
MC9S08AC48CFG@LQFP44(*) [SA245A+B4404]	
MC9S08AC48CFGE [CX3003]	
MC9S08AC48CFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AC48CFJ [CX3001]	MC9S08AC48CFJE [CX3001]
MC9S08AC48CFU [CX3014]	MC9S08AC48CFUE [CX3014]
MC9S08AC48CPU [CX3011]	MC9S08AC48CPUE [CX3011]
MC9S08AC48MFD [CX4021]	MC9S08AC48MFDE [CX4021]
MC9S08AC48MFG [CX3003]	
MC9S08AC48MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AC48MFGE [CX3003]	
MC9S08AC48MFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AC48MFJ [CX3001]	MC9S08AC48MFJE [CX3001]
MC9S08AC48MFU [CX3014]	MC9S08AC48MFUE [CX3014]
MC9S08AC48MPU [CX3011]	MC9S08AC48MPUE [CX3011]
MC9S08AC48VFD [CX4021]	MC9S08AC48VFDE [CX4021]
MC9S08AC48VFG [CX3003]	
MC9S08AC48VFG@LQFP44(*) [SA245A+B4404]	
MC9S08AC48VFGE [CX3003]	
MC9S08AC48VFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AC48VFJ [CX3001]	MC9S08AC48VFJE [CX3001]
MC9S08AC48VFU [CX3014]	MC9S08AC48VFUE [CX3014]
MC9S08AC48VPU [CX3011]	MC9S08AC48VPUE [CX3011]
MC9S08AC60CFD [CX4021]	MC9S08AC60CFDE [CX4021]
MC9S08AC60CFG [CX3003]	
MC9S08AC60CFG@LQFP44(*) [SA245A+B4404]	
MC9S08AC60CFGE [CX3003]	
MC9S08AC60CFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AC60CFJ [CX3001]	MC9S08AC60CFJE [CX3001]
MC9S08AC60CFU [CX3014]	MC9S08AC60CFUE [CX3014]
MC9S08AC60CPU [CX3011]	MC9S08AC60CPUE [CX3011]
MC9S08AC60MFD [CX4021]	MC9S08AC60MFDE [CX4021]
MC9S08AC60MFG [CX3003]	
MC9S08AC60MFG@LQFP44(*) [SA245A+B4404]	
MC9S08AC60MFGE [CX3003]	
MC9S08AC60MFGE@LQFP44(*) [SA245A+B4404]	
MC9S08AC60MFJ [CX3001]	MC9S08AC60MFJE [CX3001]
MC9S08AC60MFU [CX3014]	MC9S08AC60MFUE [CX3014]
MC9S08AC60MPU [CX3011]	MC9S08AC60MPUE [CX3011]
MC9S08AC60VFD [CX4021]	MC9S08AC60VFDE [CX4021]

MC9S08AC60VFG [CX3003]  
MC9S08AC60VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60VFGE [CX3003]  
MC9S08AC60VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC60VFJ [CX3001] MC9S08AC60VFJE [CX3001]  
MC9S08AC60VFU [CX3014] MC9S08AC60VFUE [CX3014]  
MC9S08AC60VPU [CX3011] MC9S08AC60VPUE [CX3011]  
MC9S08AC8CFD [CX4021] MC9S08AC8CFDE [CX4021]  
MC9S08AC8CFG [CX3003]  
MC9S08AC8CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8CFGE [CX3003]  
MC9S08AC8CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8CFJ [CX3001] MC9S08AC8CFJE [CX3001]  
MC9S08AC8MFD [CX4021] MC9S08AC8MFDE [CX4021]  
MC9S08AC8MFG [CX3003]  
MC9S08AC8MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8MFGE [CX3003]  
MC9S08AC8MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8MFJ [CX3001] MC9S08AC8MFJE [CX3001]  
MC9S08AC8VFD [CX4021] MC9S08AC8VFDE [CX4021]  
MC9S08AC8VFG [CX3003]  
MC9S08AC8VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8VFGE [CX3003]  
MC9S08AC8VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AC8VFJ [CX3001] MC9S08AC8VFJE [CX3001]  
MC9S08AC96CFG@QFP44 [CX3003] MC9S08AC96CFG@QFP44 [CX3003]  
MC9S08AC96CFU@QFP64 [CX3014] MC9S08AC96CFUE@QFP64 [CX3014]  
MC9S08AC96CLK@QFP80 [CX3017] MC9S08AC96CLKE@QFP80 [CX3017]  
MC9S08AC96MFG@QFP44 [CX3003] MC9S08AC96MFGE@QFP44 [CX3003]  
MC9S08AC96MFU@QFP64 [CX3014] MC9S08AC96MFUE@QFP64 [CX3014]  
MC9S08AC96MLK@QFP80 [CX3017] MC9S08AC96MLKE@QFP80 [CX3017]  
MC9S08AC96VFG@QFP44 [CX3003] MC9S08AC96VFGE@QFP44 [CX3003]  
MC9S08AC96VFU@QFP64 [CX3014] MC9S08AC96VFUE@QFP64 [CX3014]  
MC9S08AC96VLK@QFP80 [CX3017] MC9S08AC96VLKE@QFP80 [CX3017]  
MC9S08AW16CFD [CX4021] MC9S08AW16CFDE [CX4021]  
MC9S08AW16CFG [CX3003]  
MC9S08AW16CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW16CFGE [CX3003]  
MC9S08AW16CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW16CFU [CX3014] MC9S08AW16CFUE [CX3014]  
MC9S08AW16CPU [CX3011] MC9S08AW16CPUE [CX3011]  
MC9S08AW16MFD [CX4021] MC9S08AW16MFDE [CX4021]  
MC9S08AW16MFG [CX3003]  
MC9S08AW16MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW16MFGE [CX3003]  
MC9S08AW16MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW16MFU [CX3014] MC9S08AW16MFUE [CX3014]  
MC9S08AW16MPU [CX3011] MC9S08AW16MPUE [CX3011]  
MC9S08AW16VFD [CX4021] MC9S08AW16VFDE [CX4021]  
MC9S08AW16VFG [CX3003]  
MC9S08AW16VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW16VFGE [CX3003]  
MC9S08AW16VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW16VFU [CX3014] MC9S08AW16VFUE [CX3014]  
MC9S08AW16VPU [CX3011] MC9S08AW16VPUE [CX3011]  
MC9S08AW32CFD [CX4021] MC9S08AW32CFDE [CX4021]  
MC9S08AW32CFG [CX3003]  
MC9S08AW32CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW32CFGE [CX3003]

MC9S08AW32CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW32CFU [CX3014] MC9S08AW32CFUE [CX3014]  
MC9S08AW32CPU [CX3011] MC9S08AW32CPUE [CX3011]  
MC9S08AW32MFD [CX4021] MC9S08AW32MFDE [CX4021]  
MC9S08AW32MFG [CX3003]  
MC9S08AW32MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW32MFGE [CX3003]  
MC9S08AW32MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW32MFU [CX3014] MC9S08AW32MFUE [CX3014]  
MC9S08AW32MPU [CX3011] MC9S08AW32MPUE [CX3011]  
MC9S08AW32VFD [CX4021] MC9S08AW32VFDE [CX4021]  
MC9S08AW32VFG [CX3003]  
MC9S08AW32VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW32VFGE [CX3003]  
MC9S08AW32VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW32VFU [CX3014] MC9S08AW32VFUE [CX3014]  
MC9S08AW32VPU [CX3011] MC9S08AW32VPUE [CX3011]  
MC9S08AW48CFD [CX4021] MC9S08AW48CFDE [CX4021]  
MC9S08AW48CFG [CX3003]  
MC9S08AW48CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW48CFGE [CX3003]  
MC9S08AW48CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW48CFU [CX3014] MC9S08AW48CFUE [CX3014]  
MC9S08AW48CPU [CX3011] MC9S08AW48CPUE [CX3011]  
MC9S08AW48MFD [CX4021] MC9S08AW48MFDE [CX4021]  
MC9S08AW48MFG [CX3003]  
MC9S08AW48MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW48MFGE [CX3003]  
MC9S08AW48MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW48MFU [CX3014] MC9S08AW48MFUE [CX3014]  
MC9S08AW48MPU [CX3011] MC9S08AW48MPUE [CX3011]  
MC9S08AW48VFD [CX4021] MC9S08AW48VFDE [CX4021]  
MC9S08AW48VFG [CX3003]  
MC9S08AW48VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW48VFGE [CX3003]  
MC9S08AW48VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW48VFU [CX3014] MC9S08AW48VFUE [CX3014]  
MC9S08AW48VPU [CX3011] MC9S08AW48VPUE [CX3011]  
MC9S08AW60CFD [CX4021] MC9S08AW60CFDE [CX4021]  
MC9S08AW60CFG [CX3003]  
MC9S08AW60CFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW60CFGE [CX3003]  
MC9S08AW60CFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW60CFU [CX3014] MC9S08AW60CFUE [CX3014]  
MC9S08AW60CPU [CX3011] MC9S08AW60CPUE [CX3011]  
MC9S08AW60MFD [CX4021] MC9S08AW60MFDE [CX4021]  
MC9S08AW60MFG [CX3003]  
MC9S08AW60MFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW60MFGE [CX3003]  
MC9S08AW60MFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW60MFU [CX3014] MC9S08AW60MFUE [CX3014]  
MC9S08AW60MPU [CX3011] MC9S08AW60MPUE [CX3011]  
MC9S08AW60VFD [CX4021] MC9S08AW60VFDE [CX4021]  
MC9S08AW60VFG [CX3003]  
MC9S08AW60VFG@LQFP44(\*) [SA245A+B4404]  
MC9S08AW60VFGE [CX3003]  
MC9S08AW60VFGE@LQFP44(\*) [SA245A+B4404]  
MC9S08AW60VFU [CX3014] MC9S08AW60VFUE [CX3014]  
MC9S08AW60VPU [CX3011] MC9S08AW60VPUE [CX3011]





MC9S08DV32MLH@QFP64 [CX3011]	MC9S08DV32MLHE@QFP64 [CX3011]
MC9S08DV32VLC@QFP32 [CX3001]	MC9S08DV32VLCFE@QFP32 [CX3001]
MC9S08DV32VLF@QFP48 [CX3007]	MC9S08DV32VLF@QFP48 [CX3007]
MC9S08DV32VLF@QFP48 [CX3007]	MC9S08DV32VLF@QFP48 [CX3007]
MC9S08DV32VLH@QFP64 [CX3011]	MC9S08DV32VLHE@QFP64 [CX3011]
MC9S08DV48CLC@QFP32 [CX3001]	MC9S08DV48CLCE@QFP32 [CX3001]
MC9S08DV48CLF@QFP48 [CX3007]	MC9S08DV48CLFE@QFP48 [CX3007]
MC9S08DV48CLH@QFP64 [CX3011]	MC9S08DV48CLHE@QFP64 [CX3011]
MC9S08DV48MLC@QFP32 [CX3001]	MC9S08DV48MLCE@QFP32 [CX3001]
MC9S08DV48MLF@QFP48 [CX3007]	MC9S08DV48MLFE@QFP48 [CX3007]
MC9S08DV48MLH@QFP64 [CX3011]	MC9S08DV48MLHE@QFP64 [CX3011]
MC9S08DV48VLC@QFP32 [CX3001]	MC9S08DV48VLC@QFP32 [CX3001]
MC9S08DV48VLF@QFP48 [CX3007]	MC9S08DV48VLF@QFP48 [CX3007]
MC9S08DV48VLH@QFP64 [CX3011]	MC9S08DV48VLHE@QFP64 [CX3011]
MC9S08DV60CLC@QFP32 [CX3001]	MC9S08DV60CLCE@QFP32 [CX3001]
MC9S08DV60CLF@QFP48 [CX3007]	MC9S08DV60CLFE@QFP48 [CX3007]
MC9S08DV60CLH@QFP64 [CX3011]	MC9S08DV60CLHE@QFP64 [CX3011]
MC9S08DV60MLC@QFP32 [CX3001]	MC9S08DV60MLCE@QFP32 [CX3001]
MC9S08DV60MLF@QFP48 [CX3007]	MC9S08DV60MLFE@QFP48 [CX3007]
MC9S08DV60MLH@QFP64 [CX3011]	MC9S08DV60MLHE@QFP64 [CX3011]
MC9S08DV60VLC@QFP32 [CX3001]	MC9S08DV60VLC@QFP32 [CX3001]
MC9S08DV60VLF@QFP48 [CX3007]	MC9S08DV60VLF@QFP48 [CX3007]
MC9S08DV60VLH@QFP64 [CX3011]	MC9S08DV60VLHE@QFP64 [CX3011]
MC9S08DV96CLF@QFP48 [CX3007]	MC9S08DV96CLFE@QFP48 [CX3007]
MC9S08DV96CLH@QFP64 [CX3011]	MC9S08DV96CLHE@QFP64 [CX3011]
MC9S08DV96CLL@QFP100 [CX3021]	MC9S08DV96CLLE@QFP100 [CX3021]
MC9S08DV96MLF@QFP48 [CX3007]	MC9S08DV96MLFE@QFP48 [CX3007]
MC9S08DV96MLH@QFP64 [CX3011]	MC9S08DV96MLHE@QFP64 [CX3011]
MC9S08DV96MLL@QFP100 [CX3021]	MC9S08DV96MLLE@QFP100 [CX3021]
MC9S08DV96VLF@QFP48 [CX3007]	MC9S08DV96VLF@QFP48 [CX3007]
MC9S08DV96VLH@QFP64 [CX3011]	MC9S08DV96VLHE@QFP64 [CX3011]
MC9S08DV96VLL@QFP100 [CX3021]	MC9S08DV96VLL@QFP100 [CX3021]
MC9S08DZ128CLF@QFP48 [CX3007]	MC9S08DZ128CLFE@QFP48 [CX3007]
MC9S08DZ128CLH@QFP64 [CX3011]	MC9S08DZ128CLHE@QFP64 [CX3011]
MC9S08DZ128CLL@QFP100 [CX3021]	MC9S08DZ128CLLE@QFP100 [CX3021]
MC9S08DZ128MLF@QFP48 [CX3007]	MC9S08DZ128MLFE@QFP48 [CX3007]
MC9S08DZ128MLH@QFP64 [CX3011]	MC9S08DZ128MLHE@QFP64 [CX3011]
MC9S08DZ128MLL@QFP100 [CX3021]	MC9S08DZ128MLLE@QFP100 [CX3021]
MC9S08DZ128VLF@QFP48 [CX3007]	MC9S08DZ128VLF@QFP48 [CX3007]
MC9S08DZ128VLH@QFP64 [CX3011]	MC9S08DZ128VLHE@QFP64 [CX3011]
MC9S08DZ128VLL@QFP100 [CX3021]	MC9S08DZ128VLL@QFP100 [CX3021]
MC9S08DZ16CLC@QFP32 [CX3001]	MC9S08DZ16CLCE@QFP32 [CX3001]
MC9S08DZ16CLF@QFP48 [CX3007]	MC9S08DZ16CLFE@QFP48 [CX3007]
MC9S08DZ16CLH@QFP64 [CX3011]	MC9S08DZ16CLHE@QFP64 [CX3011]
MC9S08DZ16MLC@QFP32 [CX3001]	MC9S08DZ16MLCE@QFP32 [CX3001]
MC9S08DZ16MLF@QFP48 [CX3007]	MC9S08DZ16MLFE@QFP48 [CX3007]
MC9S08DZ16MLH@QFP64 [CX3011]	MC9S08DZ16MLHE@QFP64 [CX3011]
MC9S08DZ16VLC@QFP32 [CX3001]	MC9S08DZ16VLC@QFP32 [CX3001]
MC9S08DZ16VLF@QFP48 [CX3007]	MC9S08DZ16VLF@QFP48 [CX3007]
MC9S08DZ16VLH@QFP64 [CX3011]	MC9S08DZ16VLHE@QFP64 [CX3011]
MC9S08DZ32CLC@QFP32 [CX3001]	MC9S08DZ32CLCE@QFP32 [CX3001]
MC9S08DZ32CLF@QFP48 [CX3007]	MC9S08DZ32CLFE@QFP48 [CX3007]
MC9S08DZ32CLH@QFP64 [CX3011]	MC9S08DZ32CLHE@QFP64 [CX3011]
MC9S08DZ32MLC@QFP32 [CX3001]	MC9S08DZ32MLCE@QFP32 [CX3001]
MC9S08DZ32MLF@QFP48 [CX3007]	MC9S08DZ32MLFE@QFP48 [CX3007]
MC9S08DZ32MLH@QFP64 [CX3011]	MC9S08DZ32MLHE@QFP64 [CX3011]
MC9S08DZ32VLC@QFP32 [CX3001]	MC9S08DZ32VLC@QFP32 [CX3001]
MC9S08DZ32VLF@QFP48 [CX3007]	MC9S08DZ32VLF@QFP48 [CX3007]
MC9S08DZ32VLH@QFP64 [CX3011]	MC9S08DZ32VLHE@QFP64 [CX3011]
MC9S08DZ48CLC@QFP32 [CX3001]	MC9S08DZ48CLCE@QFP32 [CX3001]

MC9S08DZ48CLF@QFP48 [CX3007] MC9S08DZ48CLFE@QFP48 [CX3007]  
MC9S08DZ48CLH@QFP64 [CX3011] MC9S08DZ48CLHE@QFP64 [CX3011]  
MC9S08DZ48MLC@QFP32 [CX3001] MC9S08DZ48MLCE@QFP32 [CX3001]  
MC9S08DZ48MLF@QFP48 [CX3007] MC9S08DZ48MLFE@QFP48 [CX3007]  
MC9S08DZ48MLH@QFP64 [CX3011] MC9S08DZ48MLHE@QFP64 [CX3011]  
MC9S08DZ48VLC@QFP32 [CX3001] MC9S08DZ48VLCE@QFP32 [CX3001]  
MC9S08DZ48VLF@QFP48 [CX3007] MC9S08DZ48VLFE@QFP48 [CX3007]  
MC9S08DZ48VLH@QFP64 [CX3011] MC9S08DZ48VLHE@QFP64 [CX3011]  
MC9S08DZ60CLC@QFP32 [CX3001] MC9S08DZ60CLCE@QFP32 [CX3001]  
MC9S08DZ60CLF@QFP48 [CX3007] MC9S08DZ60CLFE@QFP48 [CX3007]  
MC9S08DZ60CLH@QFP64 [CX3011] MC9S08DZ60CLHE@QFP64 [CX3011]  
MC9S08DZ60MLC@QFP32 [CX3001] MC9S08DZ60MLCE@QFP32 [CX3001]  
MC9S08DZ60MLF@QFP48 [CX3007] MC9S08DZ60MLFE@QFP48 [CX3007]  
MC9S08DZ60MLH@QFP64 [CX3011] MC9S08DZ60MLHE@QFP64 [CX3011]  
MC9S08DZ60VLC@QFP32 [CX3001] MC9S08DZ60VLCE@QFP32 [CX3001]  
MC9S08DZ60VLF@QFP48 [CX3007] MC9S08DZ60VLFE@QFP48 [CX3007]  
MC9S08DZ60VLH@QFP64 [CX3011] MC9S08DZ60VLHE@QFP64 [CX3011]  
MC9S08DZ96CLF@QFP48 [CX3007] MC9S08DZ96CLFE@QFP48 [CX3007]  
MC9S08DZ96CLH@QFP64 [CX3011] MC9S08DZ96CLHE@QFP64 [CX3011]  
MC9S08DZ96CLL@QFP100 [CX3021] MC9S08DZ96CLLE@QFP100 [CX3021]  
MC9S08DZ96MLF@QFP48 [CX3007] MC9S08DZ96MLFE@QFP48 [CX3007]  
MC9S08DZ96MLH@QFP64 [CX3011] MC9S08DZ96MLHE@QFP64 [CX3011]  
MC9S08DZ96MLL@QFP100 [CX3021] MC9S08DZ96MLLE@QFP100 [CX3021]  
MC9S08DZ96VLF@QFP48 [CX3007] MC9S08DZ96VLFE@QFP48 [CX3007]  
MC9S08DZ96VLH@QFP64 [CX3011] MC9S08DZ96VLHE@QFP64 [CX3011]  
MC9S08DZ96VLL@QFP100 [CX3021] MC9S08DZ96VLLLE@QFP100 [CX3021]  
MC9S08EL16CTJ@TSSOP20 [CX1000] MC9S08EL16CTJE@TSSOP20 [CX1000]  
MC9S08EL16CTL@TSSOP28 [CX1001] MC9S08EL16CTLE@TSSOP28 [CX1001]  
MC9S08EL16MTJ@TSSOP20 [CX1000] MC9S08EL16MTJE@TSSOP20 [CX1000]  
MC9S08EL16MTL@TSSOP28 [CX1001] MC9S08EL16MTLE@TSSOP28 [CX1001]  
MC9S08EL16VTJ@TSSOP20 [CX1000] MC9S08EL16VTJE@TSSOP20 [CX1000]  
MC9S08EL16VTL@TSSOP28 [CX1001] MC9S08EL16VTLE@TSSOP28 [CX1001]  
MC9S08EL32CTJ@TSSOP20 [CX1000] MC9S08EL32CTJE@TSSOP20 [CX1000]  
MC9S08EL32CTL@TSSOP28 [CX1001] MC9S08EL32CTLE@TSSOP28 [CX1001]  
MC9S08EL32MTJ@TSSOP20 [CX1000] MC9S08EL32MTJE@TSSOP20 [CX1000]  
MC9S08EL32MTL@TSSOP28 [CX1001] MC9S08EL32MTLE@TSSOP28 [CX1001]  
MC9S08EL32VTJ@TSSOP20 [CX1000] MC9S08EL32VTJE@TSSOP20 [CX1000]  
MC9S08EL32VTL@TSSOP28 [CX1001] MC9S08EL32VTLE@TSSOP28 [CX1001]  
MC9S08FL16CBM@SDIP32 [CX0032]  
MC9S08FL16CBM@SDIP32(auto trim) [CX0032]  
MC9S08FL16CLC@LQFP32 [CX3001]  
MC9S08FL16CLC@LQFP32(auto trim) [CX3001]  
MC9S08FL16MBM@SDIP32 [CX0032]  
MC9S08FL16MBM@SDIP32(auto trim) [CX0032]  
MC9S08FL16MLC@LQFP32 [CX3001]  
MC9S08FL16MLC@LQFP32(auto trim) [CX3001]  
MC9S08FL16VBM@SDIP32 [CX0032]  
MC9S08FL16VBM@SDIP32(auto trim) [CX0032]  
MC9S08FL16VLC@LQFP32 [CX3001]  
MC9S08FL16VLC@LQFP32(auto trim) [CX3001]  
MC9S08FL8CBM@SDIP32 [CX0032]  
MC9S08FL8CBM@SDIP32(auto trim) [CX0032]  
MC9S08FL8CLC@LQFP32 [CX3001]  
MC9S08FL8CLC@LQFP32(auto trim) [CX3001]  
MC9S08FL8MBM@SDIP32 [CX0032]  
MC9S08FL8MBM@SDIP32(auto trim) [CX0032]  
MC9S08FL8MLC@LQFP32 [CX3001]  
MC9S08FL8MLC@LQFP32(auto trim) [CX3001]  
MC9S08FL8VBM@SDIP32 [CX0032]

MC9S08FL8VBM@SDIP32(auto trim) [CX0032]  
MC9S08FL8VLC@LQFP32 [CX3001]  
MC9S08FL8VLC@LQFP32(auto trim) [CX3001]  
MC9S08GB32ACFU@LQFP64 [CX3011]            MC9S08GB32ACFUE@LQFP64 [CX3011]  
MC9S08GB32AMFU@LQFP64 [CX3011]            MC9S08GB32AMFUE@LQFP64 [CX3011]  
MC9S08GB32AVFU@LQFP64 [CX3011]            MC9S08GB32AVFUE@LQFP64 [CX3011]  
MC9S08GB32CFU@LQFP64 [CX3011]            MC9S08GB32CFUE@LQFP64 [CX3011]  
MC9S08GB32MFU@LQFP64 [CX3011]            MC9S08GB32MFUE@LQFP64 [CX3011]  
MC9S08GB32VFU@LQFP64 [CX3011]            MC9S08GB32VFUE@LQFP64 [CX3011]  
MC9S08GB60ACFU@LQFP64 [CX3011]            MC9S08GB60ACFUE@LQFP64 [CX3011]  
MC9S08GB60AMFU@LQFP64 [CX3011]            MC9S08GB60AMFUE@LQFP64 [CX3011]  
MC9S08GB60AVFU@LQFP64 [CX3011]            MC9S08GB60AVFUE@LQFP64 [CX3011]  
MC9S08GB60CFU@LQFP64 [CX3011]            MC9S08GB60CFUE@LQFP64 [CX3011]  
MC9S08GB60MFU@LQFP64 [CX3011]            MC9S08GB60MFUE@LQFP64 [CX3011]  
MC9S08GB60VFU@LQFP64 [CX3011]            MC9S08GB60VFUE@LQFP64 [CX3011]  
MC9S08GT16ACB@SDIP42 [CX0042]            MC9S08GT16ACBE@SDIP42 [CX0042]  
MC9S08GT16ACFB@LQFP44 [CX3002]            MC9S08GT16ACFBE@LQFP44 [CX3002]  
MC9S08GT16ACFC@MLF32 [CX4015]            MC9S08GT16ACFCE@MLF32 [CX4015]  
MC9S08GT16ACFD@QFN48 [CX4021]            MC9S08GT16ACFDE@QFN48 [CX4021]  
MC9S08GT16AMB@SDIP42 [CX0042]            MC9S08GT16AMBE@SDIP42 [CX0042]  
MC9S08GT16AMFB@LQFP44 [CX3002]            MC9S08GT16AMFBE@LQFP44 [CX3002]  
MC9S08GT16AMFC@MLF32 [CX4015]            MC9S08GT16AMFCE@MLF32 [CX4015]  
MC9S08GT16AMFD@QFN48 [CX4021]            MC9S08GT16AMFDE@QFN48 [CX4021]  
MC9S08GT16AVB@SDIP42 [CX0042]            MC9S08GT16AVBE@SDIP42 [CX0042]  
MC9S08GT16AVFB@LQFP44 [CX3002]            MC9S08GT16AVFBE@LQFP44 [CX3002]  
MC9S08GT16AVFC@MLF32 [CX4015]            MC9S08GT16AVFCE@MLF32 [CX4015]  
MC9S08GT16AVFD@QFN48 [CX4021]            MC9S08GT16AVFDE@QFN48 [CX4021]  
MC9S08GT16CB@SDIP42 [CX0042]            MC9S08GT16CBE@SDIP42 [CX0042]  
MC9S08GT16CFB@LQFP44 [CX3002]            MC9S08GT16CFBE@LQFP44 [CX3002]  
MC9S08GT16CFD@QFN48 [CX4021]            MC9S08GT16CFDE@QFN48 [CX4021]  
MC9S08GT16MB@SDIP42 [CX0042]            MC9S08GT16MBE@SDIP42 [CX0042]  
MC9S08GT16MFB@LQFP44 [CX3002]            MC9S08GT16MFBE@LQFP44 [CX3002]  
MC9S08GT16MFD@QFN48 [CX4021]            MC9S08GT16MFDE@QFN48 [CX4021]  
MC9S08GT16VB@SDIP42 [CX0042]            MC9S08GT16VBE@SDIP42 [CX0042]  
MC9S08GT16VFB@LQFP44 [CX3002]            MC9S08GT16VFBE@LQFP44 [CX3002]  
MC9S08GT16VFD@QFN48 [CX4021]            MC9S08GT16VFDE@QFN48 [CX4021]  
MC9S08GT32ACB@SDIP42 [CX0042]            MC9S08GT32ACBE@SDIP42 [CX0042]  
MC9S08GT32ACFB@LQFP44 [CX3002]            MC9S08GT32ACFBE@LQFP44 [CX3002]  
MC9S08GT32ACFD@QFN48 [CX4021]            MC9S08GT32ACFDE@QFN48 [CX4021]  
MC9S08GT32AMB@SDIP42 [CX0042]            MC9S08GT32AMBE@SDIP42 [CX0042]  
MC9S08GT32AMFB@LQFP44 [CX3002]            MC9S08GT32AMFBE@LQFP44 [CX3002]  
MC9S08GT32AMFD@QFN48 [CX4021]            MC9S08GT32AMFDE@QFN48 [CX4021]  
MC9S08GT32AVB@SDIP42 [CX0042]            MC9S08GT32AVBE@SDIP42 [CX0042]  
MC9S08GT32AVFB@LQFP44 [CX3002]            MC9S08GT32AVFBE@LQFP44 [CX3002]  
MC9S08GT32AVFD@QFN48 [CX4021]            MC9S08GT32AVFDE@QFN48 [CX4021]  
MC9S08GT32CB@SDIP42 [CX0042]            MC9S08GT32CBE@SDIP42 [CX0042]  
MC9S08GT32CFB@LQFP44 [CX3002]            MC9S08GT32CFBE@LQFP44 [CX3002]  
MC9S08GT32CFD@QFN48 [CX4021]            MC9S08GT32CFDE@QFN48 [CX4021]  
MC9S08GT32MB@SDIP42 [CX0042]            MC9S08GT32MBE@SDIP42 [CX0042]  
MC9S08GT32MFB@LQFP44 [CX3002]            MC9S08GT32MFBE@LQFP44 [CX3002]  
MC9S08GT32MFD@QFN48 [CX4021]            MC9S08GT32MFDE@QFN48 [CX4021]  
MC9S08GT32VB@SDIP42 [CX0042]            MC9S08GT32VBE@SDIP42 [CX0042]  
MC9S08GT32VFB@LQFP44 [CX3002]            MC9S08GT32VFBE@LQFP44 [CX3002]  
MC9S08GT32VFD@QFN48 [CX4021]            MC9S08GT32VFDE@QFN48 [CX4021]  
MC9S08GT60ACB@SDIP42 [CX0042]            MC9S08GT60ACBE@SDIP42 [CX0042]  
MC9S08GT60ACFB@LQFP44 [CX3002]            MC9S08GT60ACFBE@LQFP44 [CX3002]  
MC9S08GT60ACFD@QFN48 [CX4021]            MC9S08GT60ACFDE@QFN48 [CX4021]  
MC9S08GT60AMB@SDIP42 [CX0042]            MC9S08GT60AMBE@SDIP42 [CX0042]  
MC9S08GT60AMFB@LQFP44 [CX3002]            MC9S08GT60AMFBE@LQFP44 [CX3002]

MC9S08GT60AMFD@QFN48 [CX4021]  
MC9S08GT60AVB@SDIP42 [CX0042]  
MC9S08GT60AVFB@LQFP44 [CX3002]  
MC9S08GT60AVFD@QFN48 [CX4021]  
MC9S08GT60CB@SDIP42 [CX0042]  
MC9S08GT60CFB@LQFP44 [CX3002]  
MC9S08GT60CFD@QFN48 [CX4021]  
MC9S08GT60MB@SDIP42 [CX0042]  
MC9S08GT60MFB@LQFP44 [CX3002]  
MC9S08GT60MFD@QFN48 [CX4021]  
MC9S08GT60VB@SDIP42 [CX0042]  
MC9S08GT60VFB@LQFP44 [CX3002]  
MC9S08GT60VFD@QFN48 [CX4021]  
MC9S08GT8ACB@SDIP42 [CX0042]  
MC9S08GT8ACFB@LQFP44 [CX3002]  
MC9S08GT8ACFC@MLF32 [CX4015]  
MC9S08GT8ACFD@QFN48 [CX4021]  
MC9S08GT8AMB@SDIP42 [CX0042]  
MC9S08GT8AMFB@LQFP44 [CX3002]  
MC9S08GT8AMFC@MLF32 [CX4015]  
MC9S08GT8AMFD@QFN48 [CX4021]  
MC9S08GT8AVB@SDIP42 [CX0042]  
MC9S08GT8AVFB@LQFP44 [CX3002]  
MC9S08GT8AVFC@MLF32 [CX4015]  
MC9S08GT8AVFD@QFN48 [CX4021]  
MC9S08JE128CLH@QFP64 [CX3011]  
MC9S08JE128MLH@QFP64 [CX3011]  
MC9S08JE128VLH@QFP64 [CX3011]  
MC9S08JE64CLH@QFP64 [CX3011]  
MC9S08JE64VLH@QFP64 [CX3011]  
MC9S08JM16CGTE@QFN48 [CX4021]  
MC9S08JM16CLCE@QFP32 [CX3001]  
MC9S08JM16CLDE@QFP44 [CX3003]  
MC9S08JM16MGTE@QFN48 [CX4021]  
MC9S08JM16MLCE@QFP32 [CX3001]  
MC9S08JM16MLDE@QFP44 [CX3003]  
MC9S08JM16VGT@QFN48 [CX4021]  
MC9S08JM16VLCE@QFP32 [CX3001]  
MC9S08JM16VLDE@QFP44 [CX3003]  
MC9S08JM32CGTE@QFN48 [CX4021]  
MC9S08JM32CLDE@QFP44 [CX3003]  
MC9S08JM32CLHE@QFP64 [CX3011]  
MC9S08JM32CQHE@QFP64 [CX3014]  
MC9S08JM32MGTE@QFN48 [CX4021]  
MC9S08JM32MLDE@QFP44 [CX3003]  
MC9S08JM32MLHE@QFP64 [CX3011]  
MC9S08JM32MQHE@QFP64 [CX3014]  
MC9S08JM32VGT@QFN48 [CX4021]  
MC9S08JM32VLDE@QFP44 [CX3003]  
MC9S08JM32VLHE@QFP64 [CX3011]  
MC9S08JM32VQHE@QFP64 [CX3014]  
MC9S08JM60CGTE@QFN48 [CX4021]  
MC9S08JM60CLDE@QFP44 [CX3003]  
MC9S08JM60CLHE@QFP64 [CX3011]  
MC9S08JM60CQHE@QFP64 [CX3014]  
MC9S08JM60MGTE@QFN48 [CX4021]  
MC9S08JM60MLDE@QFP44 [CX3003]  
MC9S08JM60MLHE@QFP64 [CX3011]  
MC9S08JM60MQHE@QFP64 [CX3014]

MC9S08GT60AMFDE@QFN48 [CX4021]  
MC9S08GT60AVBE@SDIP42 [CX0042]  
MC9S08GT60AVFBE@LQFP44 [CX3002]  
MC9S08GT60AVFDE@QFN48 [CX4021]  
MC9S08GT60CBE@SDIP42 [CX0042]  
MC9S08GT60CFBE@LQFP44 [CX3002]  
MC9S08GT60CFDE@QFN48 [CX4021]  
MC9S08GT60MBE@SDIP42 [CX0042]  
MC9S08GT60MFB@LQFP44 [CX3002]  
MC9S08GT60MFDE@QFN48 [CX4021]  
MC9S08GT60VBE@SDIP42 [CX0042]  
MC9S08GT60VFB@LQFP44 [CX3002]  
MC9S08GT60VFDE@QFN48 [CX4021]  
MC9S08GT8ACBE@SDIP42 [CX0042]  
MC9S08GT8ACFBE@LQFP44 [CX3002]  
MC9S08GT8ACFCE@MLF32 [CX4015]  
MC9S08GT8ACFDE@QFN48 [CX4021]  
MC9S08GT8AMBE@SDIP42 [CX0042]  
MC9S08GT8AMFBE@LQFP44 [CX3002]  
MC9S08GT8AMFCE@MLF32 [CX4015]  
MC9S08GT8AMFDE@QFN48 [CX4021]  
MC9S08GT8AVBE@SDIP42 [CX0042]  
MC9S08GT8AVFBE@LQFP44 [CX3002]  
MC9S08GT8AVFCE@MLF32 [CX4015]  
MC9S08GT8AVFDE@QFN48 [CX4021]  
MC9S08JE128CLK@QFP80 [CX3016]  
MC9S08JE128MLK@QFP80 [CX3016]  
MC9S08JE128VLK@QFP80 [CX3016]  
MC9S08JE64MLH@QFP64 [CX3011]  
MC9S08JM16CGT@QFN48 [CX4021]  
MC9S08JM16CLC@QFP32 [CX3001]  
MC9S08JM16CLD@QFP44 [CX3003]  
MC9S08JM16MGT@QFN48 [CX4021]  
MC9S08JM16MLC@QFP32 [CX3001]  
MC9S08JM16MLD@QFP44 [CX3003]  
MC9S08JM16VGT@QFN48 [CX4021]  
MC9S08JM16VLC@QFP32 [CX3001]  
MC9S08JM16VLD@QFP44 [CX3003]  
MC9S08JM32CGT@QFN48 [CX4021]  
MC9S08JM32CLD@QFP44 [CX3003]  
MC9S08JM32CLH@QFP64 [CX3011]  
MC9S08JM32CQH@QFP64 [CX3014]  
MC9S08JM32MGT@QFN48 [CX4021]  
MC9S08JM32MLD@QFP44 [CX3003]  
MC9S08JM32MLH@QFP64 [CX3011]  
MC9S08JM32MQH@QFP64 [CX3014]  
MC9S08JM32VGT@QFN48 [CX4021]  
MC9S08JM32VLD@QFP44 [CX3003]  
MC9S08JM32VLH@QFP64 [CX3011]  
MC9S08JM32VQH@QFP64 [CX3014]  
MC9S08JM60CGT@QFN48 [CX4021]  
MC9S08JM60CLD@QFP44 [CX3003]  
MC9S08JM60CLH@QFP64 [CX3011]  
MC9S08JM60CQH@QFP64 [CX3014]  
MC9S08JM60MGT@QFN48 [CX4021]  
MC9S08JM60MLD@QFP44 [CX3003]  
MC9S08JM60MLH@QFP64 [CX3011]  
MC9S08JM60MQH@QFP64 [CX3014]  
MC9S08JM60VGT@QFN48 [CX4021]

MC9S08JM60VGTE@QFN48 [CX4021]                    MC9S08JM60VLD@QFP44 [CX3003]  
MC9S08JM60VLDE@QFP44 [CX3003]                    MC9S08JM60VLH@QFP64 [CX3011]  
MC9S08JM60VLHE@QFP64 [CX3011]                    MC9S08JM60VQH@QFP64 [CX3014]  
MC9S08JM60VQHE@QFP64 [CX3014]                    MC9S08JM8CGT@QFN48 [CX4021]  
MC9S08JM8CGTE@QFN48 [CX4021]                    MC9S08JM8CLC@QFP32 [CX3001]  
MC9S08JM8CLCE@QFP32 [CX3001]                    MC9S08JM8CLD@QFP44 [CX3003]  
MC9S08JM8CLDE@QFP44 [CX3003]                    MC9S08JM8MGT@QFN48 [CX4021]  
MC9S08JM8MGTE@QFN48 [CX4021]                    MC9S08JM8MLC@QFP32 [CX3001]  
MC9S08JM8MLCE@QFP32 [CX3001]                    MC9S08JM8MLD@QFP44 [CX3003]  
MC9S08JM8MLDE@QFP44 [CX3003]                    MC9S08JM8VGT@QFN48 [CX4021]  
MC9S08JM8VGTE@QFN48 [CX4021]                    MC9S08JM8VLC@QFP32 [CX3001]  
MC9S08JM8VLC@QFP32 [CX3001]                    MC9S08JM8VLD@QFP44 [CX3003]  
MC9S08JM8VLDE@QFP44 [CX3003]                    MC9S08JS16CFK@QFN24 [CX4034]  
MC9S08JS16CWJ@SOIC20 [CX1033]                    MC9S08JS16LCFK@QFN24 [CX4034]  
MC9S08JS16LCWJ@SOIC20 [CX1033]                    MC9S08JS16LMFK@QFN24 [CX4034]  
MC9S08JS16LMWJ@SOIC20 [CX1033]                    MC9S08JS16LVFK@QFN24 [CX4034]  
MC9S08JS16LVWJ@SOIC20 [CX1033]                    MC9S08JS16MFK@QFN24 [CX4034]  
MC9S08JS16MWJ@SOIC20 [CX1033]                    MC9S08JS16VFK@QFN24 [CX4034]  
MC9S08JS16VWJ@SOIC20 [CX1033]                    MC9S08JS8CFK@QFN24 [CX4034]  
MC9S08JS8CWJ@SOIC20 [CX1033]                    MC9S08JS8LCFK@QFN24 [CX4034]  
MC9S08JS8LCWJ@SOIC20 [CX1033]                    MC9S08JS8LMFK@QFN24 [CX4034]  
MC9S08JS8LMWJ@SOIC20 [CX1033]                    MC9S08JS8LVFK@QFN24 [CX4034]  
MC9S08JS8LVWJ@SOIC20 [CX1033]                    MC9S08JS8MFK@QFN24 [CX4034]  
MC9S08JS8MWJ@SOIC20 [CX1033]                    MC9S08JS8VFK@QFN24 [CX4034]  
MC9S08JS8VWJ@SOIC20 [CX1033]                    MC9S08LC36LH@QFP64 [CX3011]  
MC9S08LC36LHE@QFP64 [CX3011]                    MC9S08LC36LK@QFP80 [CX3016]  
MC9S08LC36LKE@QFP80 [CX3016]                    MC9S08LC60LH@QFP64 [CX3011]  
MC9S08LC60LHE@QFP64 [CX3011]                    MC9S08LC60LK@QFP80 [CX3016]  
MC9S08LC60LKE@QFP80 [CX3016]                    MC9S08LG16CLF@QFP48 [CX3007]  
MC9S08LG16CLF@QFP48(auto trim) [CX3007]  
MC9S08LG16CLFE@QFP48 [CX3007]  
MC9S08LG16CLFE@QFP48(auto trim) [CX3007]  
MC9S08LG16CLH@QFP64 [CX3011]  
MC9S08LG16CLH@QFP64(auto trim) [CX3011]  
MC9S08LG16CLHE@QFP64 [CX3011]  
MC9S08LG16CLHE@QFP64(auto trim) [CX3011]  
MC9S08LG16MLF@QFP48 [CX3007]  
MC9S08LG16MLF@QFP48(auto trim) [CX3007]  
MC9S08LG16MLFE@QFP48 [CX3007]  
MC9S08LG16MLFE@QFP48(auto trim) [CX3007]  
MC9S08LG16MLH@QFP64 [CX3011]  
MC9S08LG16MLH@QFP64(auto trim) [CX3011]  
MC9S08LG16MLHE@QFP64 [CX3011]  
MC9S08LG16MLHE@QFP64(auto trim) [CX3011]  
MC9S08LG16VLF@QFP48 [CX3007]  
MC9S08LG16VLF@QFP48(auto trim) [CX3007]  
MC9S08LG16VLFE@QFP48 [CX3007]  
MC9S08LG16VLFE@QFP48(auto trim) [CX3007]  
MC9S08LG16VLH@QFP64 [CX3011]  
MC9S08LG16VLH@QFP64(auto trim) [CX3011]  
MC9S08LG16VLHE@QFP64 [CX3011]  
MC9S08LG16VLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32CLF@QFP48 [CX3007]  
MC9S08LG32CLF@QFP48(auto trim) [CX3007]  
MC9S08LG32CLFE@QFP48 [CX3007]  
MC9S08LG32CLFE@QFP48(auto trim) [CX3007]  
MC9S08LG32CLH@QFP64 [CX3011]  
MC9S08LG32CLH@QFP64(auto trim) [CX3011]  
MC9S08LG32CLHE@QFP64 [CX3011]

MC9S08LG32CLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32CLK@QFP80 [CX3017]  
MC9S08LG32CLK@QFP80(auto trim) [CX3017]  
MC9S08LG32CLKE@QFP80 [CX3017]  
MC9S08LG32CLKE@QFP80(auto trim) [CX3017]  
MC9S08LG32MLF@QFP48 [CX3007]  
MC9S08LG32MLF@QFP48(auto trim) [CX3007]  
MC9S08LG32MLFE@QFP48 [CX3007]  
MC9S08LG32MLFE@QFP48(auto trim) [CX3007]  
MC9S08LG32MLH@QFP64 [CX3011]  
MC9S08LG32MLH@QFP64(auto trim) [CX3011]  
MC9S08LG32MLHE@QFP64 [CX3011]  
MC9S08LG32MLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32MLK@QFP80 [CX3017]  
MC9S08LG32MLK@QFP80(auto trim) [CX3017]  
MC9S08LG32MLKE@QFP80 [CX3017]  
MC9S08LG32MLKE@QFP80(auto trim) [CX3017]  
MC9S08LG32VLF@QFP48 [CX3007]  
MC9S08LG32VLF@QFP48(auto trim) [CX3007]  
MC9S08LG32VLFE@QFP48 [CX3007]  
MC9S08LG32VLFE@QFP48(auto trim) [CX3007]  
MC9S08LG32VLH@QFP64 [CX3011]  
MC9S08LG32VLH@QFP64(auto trim) [CX3011]  
MC9S08LG32VLHE@QFP64 [CX3011]  
MC9S08LG32VLHE@QFP64(auto trim) [CX3011]  
MC9S08LG32VLK@QFP80 [CX3017]  
MC9S08LG32VLK@QFP80(auto trim) [CX3017]  
MC9S08LG32VLKE@QFP80 [CX3017]  
MC9S08LG32VLKE@QFP80(auto trim) [CX3017]  
MC9S08LL16CGT@QFN48 [CX4021]  
MC9S08LL16CGT@QFN48(auto trim) [CX4021]  
MC9S08LL16CLF@LQFP48 [CX3007]  
MC9S08LL16CLF@LQFP48(auto trim) [CX3007]  
MC9S08LL16CLH@LQFP64 [CX3011]  
MC9S08LL16CLH@LQFP64(auto trim) [CX3011]  
MC9S08LL16MGT@QFN48 [CX4021]  
MC9S08LL16MGT@QFN48(auto trim) [CX4021]  
MC9S08LL16MLF@LQFP48 [CX3007]  
MC9S08LL16MLF@LQFP48(auto trim) [CX3007]  
MC9S08LL16MLH@LQFP64 [CX3011]  
MC9S08LL16MLH@LQFP64(auto trim) [CX3011]  
MC9S08LL16VGT@QFN48 [CX4021]  
MC9S08LL16VGT@QFN48(auto trim) [CX4021]  
MC9S08LL16VLF@LQFP48 [CX3007]  
MC9S08LL16VLF@LQFP48(auto trim) [CX3007]  
MC9S08LL16VLH@LQFP64 [CX3011]  
MC9S08LL16VLH@LQFP64(auto trim) [CX3011]  
MC9S08LL64CLH@LQFP64 [CX3011]           MC9S08LL64CLK@QFP80 [CX3017]  
MC9S08LL64MLH@LQFP64 [CX3011]           MC9S08LL64MLK@QFP80 [CX3017]  
MC9S08LL64VLH@LQFP64 [CX3011]           MC9S08LL64VLK@QFP80 [CX3017]  
MC9S08LL8CGT@QFN48 [CX4021]  
MC9S08LL8CGT@QFN48(auto trim) [CX4021]  
MC9S08LL8CLF@LQFP48 [CX3007]  
MC9S08LL8CLF@LQFP48(auto trim) [CX3007]  
MC9S08LL8CLH@LQFP64 [CX3011]  
MC9S08LL8CLH@LQFP64(auto trim) [CX3011]  
MC9S08LL8MGT@QFN48 [CX4021]  
MC9S08LL8MGT@QFN48(auto trim) [CX4021]  
MC9S08LL8MLF@LQFP48 [CX3007]

MC9S08LL8MLF@LQFP48(auto trim) [CX3007]  
MC9S08LL8MLH@LQFP64 [CX3011]  
MC9S08LL8MLH@LQFP64(auto trim) [CX3011]  
MC9S08LL8VGT@QFN48 [CX4021]  
MC9S08LL8VGT@QFN48(auto trim) [CX4021]  
MC9S08LL8VLF@LQFP48 [CX3007]  
MC9S08LL8VLF@LQFP48(auto trim) [CX3007]  
MC9S08LL8VLH@LQFP64 [CX3011]  
MC9S08LL8VLH@LQFP64(auto trim) [CX3011]  
MC9S08PA16CLC [CX3001] MC9S08PA16CLD [CX3005]  
MC9S08PA16CTG [CX1000] MC9S08PA16CTJ [CX1000]  
MC9S08PA16CWJ [CX1033] MC9S08PA16VLC [CX3001]  
MC9S08PA16VLD [CX3005] MC9S08PA16VTG [CX1000]  
MC9S08PA16VTJ [CX1000] MC9S08PA16VWJ [CX1033]  
MC9S08PA32CLC [CX3001] MC9S08PA32CLD [CX3005]  
MC9S08PA32CLF [CX3007] MC9S08PA32CLH [CX3011]  
MC9S08PA32CQH [CX3014] MC9S08PA32VLC [CX3001]  
MC9S08PA32VLD [CX3005] MC9S08PA32VLF [CX3007]  
MC9S08PA32VLH [CX3011] MC9S08PA32VQH [CX3014]  
MC9S08PA60CLC [CX3001] MC9S08PA60CLD [CX3005]  
MC9S08PA60CLF [CX3007] MC9S08PA60CLH [CX3011]  
MC9S08PA60CQH [CX3014] MC9S08PA60VLC [CX3001]  
MC9S08PA60VLD [CX3005] MC9S08PA60VLF [CX3007]  
MC9S08PA60VLH [CX3011] MC9S08PA60VQH [CX3014]  
MC9S08PA8CLC [CX3001] MC9S08PA8CLD [CX3005]  
MC9S08PA8CTG [CX1000] MC9S08PA8CTJ [CX1000]  
MC9S08PA8CWJ [CX1033] MC9S08PA8VLC [CX3001]  
MC9S08PA8VLD [CX3005] MC9S08PA8VTG [CX1000]  
MC9S08PA8VTJ [CX1000] MC9S08PA8VWJ [CX1033]  
MC9S08PT16CLC [CX3001] MC9S08PT16CLD [CX3005]  
MC9S08PT16CTG [CX1000] MC9S08PT16CTJ [CX1000]  
MC9S08PT16CWJ [CX1033] MC9S08PT16VLC [CX3001]  
MC9S08PT16VLD [CX3005] MC9S08PT16VTG [CX1000]  
MC9S08PT16VTJ [CX1000] MC9S08PT16VWJ [CX1033]  
MC9S08PT32CLC [CX3001] MC9S08PT32CLD [CX3005]  
MC9S08PT32CLF [CX3007] MC9S08PT32CLH [CX3011]  
MC9S08PT32CQH [CX3014] MC9S08PT32VLC [CX3001]  
MC9S08PT32VLD [CX3005] MC9S08PT32VLF [CX3007]  
MC9S08PT32VLH [CX3011] MC9S08PT32VQH [CX3014]  
MC9S08PT60CLC [CX3001] MC9S08PT60CLD [CX3005]  
MC9S08PT60CLF [CX3007] MC9S08PT60CLH [CX3011]  
MC9S08PT60CQH [CX3014] MC9S08PT60VLC [CX3001]  
MC9S08PT60VLD [CX3005] MC9S08PT60VLF [CX3007]  
MC9S08PT60VLH [CX3011] MC9S08PT60VQH [CX3014]  
MC9S08PT8CLC [CX3001] MC9S08PT8CLD [CX3005]  
MC9S08PT8CTG [CX1000] MC9S08PT8CTJ [CX1000]  
MC9S08PT8CWJ [CX1033] MC9S08PT8VLC [CX3001]  
MC9S08PT8VLD [CX3005] MC9S08PT8VTG [CX1000]  
MC9S08PT8VTJ [CX1000] MC9S08PT8VWJ [CX1033]  
MC9S08QA2CDN@SOIC8 [CX1030] MC9S08QA2CDNE@SOIC8 [CX1030]  
MC9S08QA2CFQ@DFN8 [CX4004] MC9S08QA2CFQE@DFN8 [CX4004]  
MC9S08QA2CPA MC9S08QA2CPAE  
MC9S08QA2MDN@SOIC8 [CX1030] MC9S08QA2MDNE@SOIC8 [CX1030]  
MC9S08QA2MFQ@DFN8 [CX4004] MC9S08QA2MFQE@DFN8 [CX4004]  
MC9S08QA2MPA MC9S08QA2MPAE  
MC9S08QA2VDN@SOIC8 [CX1030] MC9S08QA2VDNE@SOIC8 [CX1030]  
MC9S08QA2VFQ@DFN8 [CX4004] MC9S08QA2VFQE@DFN8 [CX4004]  
MC9S08QA2VPA MC9S08QA2VPAE  
MC9S08QA4CDN@SOIC8 [CX1030] MC9S08QA4CDNE@SOIC8 [CX1030]



MC9S08QA4CFQ@DFN8 [CX4004]                    MC9S08QA4CFQE@DFN8 [CX4004]  
MC9S08QA4CPA                                    MC9S08QA4CPAE  
MC9S08QA4MDN@SOIC8 [CX1030]                   MC9S08QA4MDNE@SOIC8 [CX1030]  
MC9S08QA4MFQ@DFN8 [CX4004]                   MC9S08QA4MFQE@DFN8 [CX4004]  
MC9S08QA4MPA                                    MC9S08QA4MPAE  
MC9S08QA4VDN@SOIC8 [CX1030]                   MC9S08QA4VDNE@SOIC8 [CX1030]  
MC9S08QA4VFQ@DFN8 [CX4004]                   MC9S08QA4VFQE@DFN8 [CX4004]  
MC9S08QA4VPA                                    MC9S08QA4VPAE  
MC9S08QB4CGK@QFN24 [CX4034]                   MC9S08QB4CTG@TSSOP16 [CX1001]  
MC9S08QB4CWL@SOIC28 [CX1033]                   MC9S08QB4MGK@QFN24 [CX4034]  
MC9S08QB4MTG@TSSOP16 [CX1001]                   MC9S08QB4MWL@SOIC28 [CX1033]  
MC9S08QB4VGK@QFN24 [CX4034]                   MC9S08QB4VTG@TSSOP16 [CX1001]  
MC9S08QB4VWL@SOIC28 [CX1033]                   MC9S08QB8CGK@QFN24 [CX4034]  
MC9S08QB8CTG@TSSOP16 [CX1001]                   MC9S08QB8CWL@SOIC28 [CX1033]  
MC9S08QB8MGK@QFN24 [CX4034]                   MC9S08QB8MTG@TSSOP16 [CX1001]  
MC9S08QB8MWL@SOIC28 [CX1033]                   MC9S08QB8VGK@QFN24 [CX4034]  
MC9S08QB8VTG@TSSOP16 [CX1001]                   MC9S08QB8VWL@SOIC28 [CX1033]  
MC9S08QD2CPC                                    MC9S08QD2CPCE  
MC9S08QD2CSC@SOIC8 [CX1016]                   MC9S08QD2CSCE@SOIC8 [CX1016]  
MC9S08QD2MPC                                    MC9S08QD2MPCE  
MC9S08QD2MSC@SOIC8 [CX1016]                   MC9S08QD2MSCE@SOIC8 [CX1016]  
MC9S08QD2VPC                                    MC9S08QD2VPCE  
MC9S08QD2VSC@SOIC8 [CX1016]                   MC9S08QD2VSCE@SOIC8 [CX1016]  
MC9S08QD4CPC                                    MC9S08QD4CPCE  
MC9S08QD4CSC@SOIC8 [CX1016]                   MC9S08QD4CSCE@SOIC8 [CX1016]  
MC9S08QD4MPC                                    MC9S08QD4MPCE  
MC9S08QD4MSC@SOIC8 [CX1016]                   MC9S08QD4MSCE@SOIC8 [CX1016]  
MC9S08QD4VPC                                    MC9S08QD4VPCE  
MC9S08QD4VSC@SOIC8 [CX1016]                   MC9S08QD4VSCE@SOIC8 [CX1016]  
MC9S08QE128CFT@QFN48 [CX4021]                   MC9S08QE128CFTE@QFN48 [CX4021]  
MC9S08QE128CLC@QFP32 [CX3001]                   MC9S08QE128CLCE@QFP32 [CX3001]  
MC9S08QE128CLD@QFP44 [CX3005]                   MC9S08QE128CLDE@QFP44 [CX3005]  
MC9S08QE128CLH@QFP64 [CX3011]                   MC9S08QE128CLHE@QFP64 [CX3011]  
MC9S08QE128CLK@QFP80 [CX3017]                   MC9S08QE128CLKE@QFP80 [CX3017]  
MC9S08QE128MFT@QFN48 [CX4021]                   MC9S08QE128MFTE@QFN48 [CX4021]  
MC9S08QE128MLC@QFP32 [CX3001]                   MC9S08QE128MLCE@QFP32 [CX3001]  
MC9S08QE128MLD@QFP44 [CX3005]                   MC9S08QE128MLDE@QFP44 [CX3005]  
MC9S08QE128MLH@QFP64 [CX3011]                   MC9S08QE128MLHE@QFP64 [CX3011]  
MC9S08QE128MLK@QFP80 [CX3017]                   MC9S08QE128MLKE@QFP80 [CX3017]  
MC9S08QE128VFT@QFN48 [CX4021]                   MC9S08QE128VFTE@QFN48 [CX4021]  
MC9S08QE128VLC@QFP32 [CX3001]                   MC9S08QE128VLC@QFP32 [CX3001]  
MC9S08QE128VLD@QFP44 [CX3005]                   MC9S08QE128VLDE@QFP44 [CX3005]  
MC9S08QE128VLH@QFP64 [CX3011]                   MC9S08QE128VLHE@QFP64 [CX3011]  
MC9S08QE128VLK@QFP80 [CX3017]                   MC9S08QE128VLKE@QFP80 [CX3017]  
MC9S08QE16CFT@QFN48 [CX4021]  
MC9S08QE16CFT@QFN48(auto trim) [CX4021]  
MC9S08QE16CFTE@QFN48 [CX4021]  
MC9S08QE16CFTE@QFN48(auto trim) [CX4021]  
MC9S08QE16CLC@QFP32 [CX3001]  
MC9S08QE16CLC@QFP32(auto trim) [CX3001]  
MC9S08QE16CLCE@QFP32 [CX3001]  
MC9S08QE16CLCE@QFP32(auto trim) [CX3001]  
MC9S08QE16CLD@QFP44 [CX3005]  
MC9S08QE16CLD@QFP44(auto trim) [CX3005]  
MC9S08QE16CLDE@QFP44 [CX3005]  
MC9S08QE16CLDE@QFP44(auto trim) [CX3005]  
MC9S08QE16CWL@SOIC28 [CX1033]  
MC9S08QE16CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE16CWLE@SOIC28 [CX1033]

MC9S08QE16CWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE16MFT@QFN48 [CX4021]  
MC9S08QE16MFT@QFN48(auto trim) [CX4021]  
MC9S08QE16MFTE@QFN48 [CX4021]  
MC9S08QE16MFTE@QFN48(auto trim) [CX4021]  
MC9S08QE16MLC@QFP32 [CX3001]  
MC9S08QE16MLC@QFP32(auto trim) [CX3001]  
MC9S08QE16MLCE@QFP32 [CX3001]  
MC9S08QE16MLCE@QFP32(auto trim) [CX3001]  
MC9S08QE16MLD@QFP44 [CX3005]  
MC9S08QE16MLD@QFP44(auto trim) [CX3005]  
MC9S08QE16MLDE@QFP44 [CX3005]  
MC9S08QE16MLDE@QFP44(auto trim) [CX3005]  
MC9S08QE16MWL@SOIC28 [CX1033]  
MC9S08QE16MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE16MWLE@SOIC28 [CX1033]  
MC9S08QE16MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE16VFT@QFN48 [CX4021]  
MC9S08QE16VFT@QFN48(auto trim) [CX4021]  
MC9S08QE16VFTE@QFN48 [CX4021]  
MC9S08QE16VFTE@QFN48(auto trim) [CX4021]  
MC9S08QE16VLC@QFP32 [CX3001]  
MC9S08QE16VLC@QFP32(auto trim) [CX3001]  
MC9S08QE16VLC@QFP32 [CX3001]  
MC9S08QE16VLC@QFP32(auto trim) [CX3001]  
MC9S08QE16VLD@QFP44 [CX3005]  
MC9S08QE16VLD@QFP44(auto trim) [CX3005]  
MC9S08QE16VLDE@QFP44 [CX3005]  
MC9S08QE16VLDE@QFP44(auto trim) [CX3005]  
MC9S08QE16VWL@SOIC28 [CX1033]  
MC9S08QE16VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE16VWLE@SOIC28 [CX1033]  
MC9S08QE16VWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE32CFT@QFN48 [CX4021]  
MC9S08QE32CFT@QFN48(auto trim) [CX4021]  
MC9S08QE32CFTE@QFN48 [CX4021]  
MC9S08QE32CFTE@QFN48(auto trim) [CX4021]  
MC9S08QE32CLC@QFP32 [CX3001]  
MC9S08QE32CLC@QFP32(auto trim) [CX3001]  
MC9S08QE32CLCE@QFP32 [CX3001]  
MC9S08QE32CLCE@QFP32(auto trim) [CX3001]  
MC9S08QE32CLD@QFP44 [CX3005]  
MC9S08QE32CLD@QFP44(auto trim) [CX3005]  
MC9S08QE32CLDE@QFP44 [CX3005]  
MC9S08QE32CLDE@QFP44(auto trim) [CX3005]  
MC9S08QE32CWL@SOIC28 [CX1033]  
MC9S08QE32CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE32CWLE@SOIC28 [CX1033]  
MC9S08QE32CWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE32MFT@QFN48 [CX4021]  
MC9S08QE32MFT@QFN48(auto trim) [CX4021]  
MC9S08QE32MFTE@QFN48 [CX4021]  
MC9S08QE32MFTE@QFN48(auto trim) [CX4021]  
MC9S08QE32MLC@QFP32 [CX3001]  
MC9S08QE32MLC@QFP32(auto trim) [CX3001]  
MC9S08QE32MLCE@QFP32 [CX3001]  
MC9S08QE32MLCE@QFP32(auto trim) [CX3001]  
MC9S08QE32MLD@QFP44 [CX3005]  
MC9S08QE32MLD@QFP44(auto trim) [CX3005]

MC9S08QE32MLDE@QFP44 [CX3005]  
MC9S08QE32MLDE@QFP44(auto trim) [CX3005]  
MC9S08QE32MWL@SOIC28 [CX1033]  
MC9S08QE32MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE32MWLE@SOIC28 [CX1033]  
MC9S08QE32MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE32VFT@QFN48 [CX4021]  
MC9S08QE32VFT@QFN48(auto trim) [CX4021]  
MC9S08QE32VFTE@QFN48 [CX4021]  
MC9S08QE32VFTE@QFN48(auto trim) [CX4021]  
MC9S08QE32VLC@QFP32 [CX3001]  
MC9S08QE32VLC@QFP32(auto trim) [CX3001]  
MC9S08QE32VLCE@QFP32 [CX3001]  
MC9S08QE32VLCE@QFP32(auto trim) [CX3001]  
MC9S08QE32VLD@QFP44 [CX3005]  
MC9S08QE32VLD@QFP44(auto trim) [CX3005]  
MC9S08QE32VLDE@QFP44 [CX3005]  
MC9S08QE32VLDE@QFP44(auto trim) [CX3005]  
MC9S08QE32VWL@SOIC28 [CX1033]  
MC9S08QE32VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE32VWLE@SOIC28 [CX1033]  
MC9S08QE32VWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE4CLC@QFP32 [CX3001]  
MC9S08QE4CLC@QFP32(auto trim) [CX3001]  
MC9S08QE4CLCE@QFP32 [CX3001]  
MC9S08QE4CLCE@QFP32(auto trim) [CX3001]  
MC9S08QE4CPG MC9S08QE4CPG(auto trim)  
MC9S08QE4CPGE MC9S08QE4CPGE(auto trim)  
MC9S08QE4CTG@TSSOP16 [CX1000]  
MC9S08QE4CTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE4CTGE@TSSOP16 [CX1000]  
MC9S08QE4CTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE4CWJ@SOIC20 [CX1033]  
MC9S08QE4CWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE4CWJE@SOIC20 [CX1033]  
MC9S08QE4CWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE4CWL@SOIC28 [CX1033]  
MC9S08QE4CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE4CWLE@SOIC28 [CX1033]  
MC9S08QE4CWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE4MLC@QFP32 [CX3001]  
MC9S08QE4MLC@QFP32(auto trim) [CX3001]  
MC9S08QE4MLCE@QFP32 [CX3001]  
MC9S08QE4MLCE@QFP32(auto trim) [CX3001]  
MC9S08QE4MPG MC9S08QE4MPG(auto trim)  
MC9S08QE4MPGE MC9S08QE4MPGE(auto trim)  
MC9S08QE4MTG@TSSOP16 [CX1000]  
MC9S08QE4MTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE4MTGE@TSSOP16 [CX1000]  
MC9S08QE4MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE4MWJ@SOIC20 [CX1033]  
MC9S08QE4MWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE4MWJE@SOIC20 [CX1033]  
MC9S08QE4MWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE4MWL@SOIC28 [CX1033]  
MC9S08QE4MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE4MWLE@SOIC28 [CX1033]  
MC9S08QE4MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE4VLC@QFP32 [CX3001]

MC9S08QE4VLC@QFP32(auto trim) [CX3001]  
MC9S08QE4VLC@QFP32 [CX3001]  
MC9S08QE4VLC@QFP32(auto trim) [CX3001]  
MC9S08QE4VPG MC9S08QE4VPG(auto trim)  
MC9S08QE4VPG MC9S08QE4VPGE(auto trim)  
MC9S08QE4VTG@TSSOP16 [CX1000]  
MC9S08QE4VTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE4VTG@TSSOP16 [CX1000]  
MC9S08QE4VTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE4VWJ@SOIC20 [CX1033]  
MC9S08QE4VWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE4VWJ@SOIC20 [CX1033]  
MC9S08QE4VWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE4VWL@SOIC28 [CX1033]  
MC9S08QE4VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE4VWL@SOIC28 [CX1033]  
MC9S08QE4VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE64CFT@QFN48 [CX4021] MC9S08QE64CFT@QFN48 [CX4021]  
MC9S08QE64CLC@QFP32 [CX3001] MC9S08QE64CLC@QFP32 [CX3001]  
MC9S08QE64CLD@QFP44 [CX3005] MC9S08QE64CLD@QFP44 [CX3005]  
MC9S08QE64CLH@QFP64 [CX3011] MC9S08QE64CLH@QFP64 [CX3011]  
MC9S08QE64CLK@QFP80 [CX3017] MC9S08QE64CLK@QFP80 [CX3017]  
MC9S08QE64MFT@QFN48 [CX4021] MC9S08QE64MFT@QFN48 [CX4021]  
MC9S08QE64MLC@QFP32 [CX3001] MC9S08QE64MLC@QFP32 [CX3001]  
MC9S08QE64MLD@QFP44 [CX3005] MC9S08QE64MLD@QFP44 [CX3005]  
MC9S08QE64MLH@QFP64 [CX3011] MC9S08QE64MLH@QFP64 [CX3011]  
MC9S08QE64MLK@QFP80 [CX3017] MC9S08QE64MLK@QFP80 [CX3017]  
MC9S08QE64VFT@QFN48 [CX4021] MC9S08QE64VFT@QFN48 [CX4021]  
MC9S08QE64VLC@QFP32 [CX3001] MC9S08QE64VLC@QFP32 [CX3001]  
MC9S08QE64VLD@QFP44 [CX3005] MC9S08QE64VLD@QFP44 [CX3005]  
MC9S08QE64VLH@QFP64 [CX3011] MC9S08QE64VLH@QFP64 [CX3011]  
MC9S08QE64VLK@QFP80 [CX3017] MC9S08QE64VLK@QFP80 [CX3017]  
MC9S08QE8CLC@QFP32 [CX3001]  
MC9S08QE8CLC@QFP32(auto trim) [CX3001]  
MC9S08QE8CLC@QFP32 [CX3001]  
MC9S08QE8CLC@QFP32(auto trim) [CX3001]  
MC9S08QE8CPG MC9S08QE8CPG(auto trim)  
MC9S08QE8CPG MC9S08QE8CPG(auto trim)  
MC9S08QE8CTG@TSSOP16 [CX1000]  
MC9S08QE8CTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE8CTG@TSSOP16 [CX1000]  
MC9S08QE8CTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE8CWJ@SOIC20 [CX1033]  
MC9S08QE8CWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE8CWJ@SOIC20 [CX1033]  
MC9S08QE8CWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE8CWL@SOIC28 [CX1033]  
MC9S08QE8CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE8CWL@SOIC28 [CX1033]  
MC9S08QE8CWL@SOIC28(auto trim) [CX1033]  
MC9S08QE8MLC@QFP32 [CX3001]  
MC9S08QE8MLC@QFP32(auto trim) [CX3001]  
MC9S08QE8MLC@QFP32 [CX3001]  
MC9S08QE8MLC@QFP32(auto trim) [CX3001]  
MC9S08QE8MPG MC9S08QE8MPG(auto trim)  
MC9S08QE8MPG MC9S08QE8MPG(auto trim)  
MC9S08QE8MTG@TSSOP16 [CX1000]  
MC9S08QE8MTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE8MTG@TSSOP16 [CX1000]

MC9S08QE8MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE8MWJ@SOIC20 [CX1033]  
MC9S08QE8MWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE8MWJE@SOIC20 [CX1033]  
MC9S08QE8MWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE8MWL@SOIC28 [CX1033]  
MC9S08QE8MWL@SOIC28(auto trim) [CX1033]  
MC9S08QE8MWLE@SOIC28 [CX1033]  
MC9S08QE8MWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE8VLC@QFP32 [CX3001]  
MC9S08QE8VLC@QFP32(auto trim) [CX3001]  
MC9S08QE8VLC@QFP32 [CX3001]  
MC9S08QE8VLC@QFP32(auto trim) [CX3001]  
MC9S08QE8VPG MC9S08QE8VPG(auto trim)  
MC9S08QE8VPGE MC9S08QE8VPGE(auto trim)  
MC9S08QE8VTG@TSSOP16 [CX1000]  
MC9S08QE8VTG@TSSOP16(auto trim) [CX1000]  
MC9S08QE8VTGE@TSSOP16 [CX1000]  
MC9S08QE8VTGE@TSSOP16(auto trim) [CX1000]  
MC9S08QE8VWJ@SOIC20 [CX1033]  
MC9S08QE8VWJ@SOIC20(auto trim) [CX1033]  
MC9S08QE8VWJE@SOIC20 [CX1033]  
MC9S08QE8VWJE@SOIC20(auto trim) [CX1033]  
MC9S08QE8VWL@SOIC28 [CX1033]  
MC9S08QE8VWL@SOIC28(auto trim) [CX1033]  
MC9S08QE8VWLE@SOIC28 [CX1033]  
MC9S08QE8VWLE@SOIC28(auto trim) [CX1033]  
MC9S08QE96CFT@QFN48 [CX4021] MC9S08QE96CFTE@QFN48 [CX4021]  
MC9S08QE96CLC@QFP32 [CX3001] MC9S08QE96CLCE@QFP32 [CX3001]  
MC9S08QE96CLD@QFP44 [CX3005] MC9S08QE96CLDE@QFP44 [CX3005]  
MC9S08QE96CLH@QFP64 [CX3011] MC9S08QE96CLHE@QFP64 [CX3011]  
MC9S08QE96CLK@QFP80 [CX3017] MC9S08QE96CLKE@QFP80 [CX3017]  
MC9S08QE96MFT@QFN48 [CX4021] MC9S08QE96MFTE@QFN48 [CX4021]  
MC9S08QE96MLC@QFP32 [CX3001] MC9S08QE96MLCE@QFP32 [CX3001]  
MC9S08QE96MLD@QFP44 [CX3005] MC9S08QE96MLDE@QFP44 [CX3005]  
MC9S08QE96MLH@QFP64 [CX3011] MC9S08QE96MLHE@QFP64 [CX3011]  
MC9S08QE96MLK@QFP80 [CX3017] MC9S08QE96MLKE@QFP80 [CX3017]  
MC9S08QE96VFT@QFN48 [CX4021] MC9S08QE96VFTE@QFN48 [CX4021]  
MC9S08QE96VLC@QFP32 [CX3001] MC9S08QE96VLC@QFP32 [CX3001]  
MC9S08QE96VLD@QFP44 [CX3005] MC9S08QE96VLDE@QFP44 [CX3005]  
MC9S08QE96VLH@QFP64 [CX3011] MC9S08QE96VLHE@QFP64 [CX3011]  
MC9S08QE96VLK@QFP80 [CX3017] MC9S08QE96VLKE@QFP80 [CX3017]  
MC9S08QG4CDN@SOIC8 [CX1030] MC9S08QG4CDNE@SOIC8 [CX1030]  
MC9S08QG4CDT@TSSOP16 [CX1000] MC9S08QG4CDTE@TSSOP16 [CX1000]  
MC9S08QG4CFF@QFN16 [CX4009] MC9S08QG4CFFE@QFN16 [CX4009]  
MC9S08QG4CFQ@DFN8 [CX4004] MC9S08QG4CFQE@DFN8 [CX4004]  
MC9S08QG4CPAE  
MC9S08QG4MDN@SOIC8 [CX1030] MC9S08QG4MDNE@SOIC8 [CX1030]  
MC9S08QG4MDT@TSSOP16 [CX1000] MC9S08QG4MDTE@TSSOP16 [CX1000]  
MC9S08QG4MFF@QFN16 [CX4009] MC9S08QG4MFFE@QFN16 [CX4009]  
MC9S08QG4MFQ@DFN8 [CX4004] MC9S08QG4MFQE@DFN8 [CX4004]  
MC9S08QG4MPAE  
MC9S08QG4VDN@SOIC8 [CX1030] MC9S08QG4VDNE@SOIC8 [CX1030]  
MC9S08QG4VDT@TSSOP16 [CX1000] MC9S08QG4VDTE@TSSOP16 [CX1000]  
MC9S08QG4VFF@QFN16 [CX4009] MC9S08QG4VFFE@QFN16 [CX4009]  
MC9S08QG4VFQ@DFN8 [CX4004] MC9S08QG4VFQE@DFN8 [CX4004]  
MC9S08QG4VPAE  
MC9S08QG8CDN@SOIC8 [CX1030] MC9S08QG8CDNE@SOIC8 [CX1030]  
MC9S08QG8CDT@TSSOP16 [CX1000] MC9S08QG8CDTE@TSSOP16 [CX1000]

MC9S08QG8CFF@QFN16 [CX4009]  
MC9S08QG8CFQ@DFN8 [CX4004]  
MC9S08QG8CPB  
MC9S08QG8MDN@SOIC8 [CX1030]  
MC9S08QG8MDT@TSSOP16 [CX1000]  
MC9S08QG8MFF@QFN16 [CX4009]  
MC9S08QG8MFQ@DFN8 [CX4004]  
MC9S08QG8MPB  
MC9S08QG8VDN@SOIC8 [CX1030]  
MC9S08QG8VDT@TSSOP16 [CX1000]  
MC9S08QG8VFF@QFN16 [CX4009]  
MC9S08QG8VFQ@DFN8 [CX4004]  
MC9S08QG8VPB  
MC9S08RC16CDW@SOIC28 [CX1033]  
MC9S08RC16CFD@QFN48 [CX4021]  
MC9S08RC16CFG@LQFP44 [CX3003]  
MC9S08RC16CFJ@LQFP32 [CX3001]  
MC9S08RC16CP  
MC9S08RC16MDW@SOIC28 [CX1033]  
MC9S08RC16MFD@QFN48 [CX4021]  
MC9S08RC16MFG@LQFP44 [CX3003]  
MC9S08RC16MFJ@LQFP32 [CX3001]  
MC9S08RC16MP  
MC9S08RC16VDW@SOIC28 [CX1033]  
MC9S08RC16VFD@QFN48 [CX4021]  
MC9S08RC16VFG@LQFP44 [CX3003]  
MC9S08RC16VFJ@LQFP32 [CX3001]  
MC9S08RC16VP  
MC9S08RC32CDW@SOIC28 [CX1033]  
MC9S08RC32CFD@QFN48 [CX4021]  
MC9S08RC32CFG@LQFP44 [CX3003]  
MC9S08RC32CFJ@LQFP32 [CX3001]  
MC9S08RC32CP  
MC9S08RC32MDW@SOIC28 [CX1033]  
MC9S08RC32MFD@QFN48 [CX4021]  
MC9S08RC32MFG@LQFP44 [CX3003]  
MC9S08RC32MFJ@LQFP32 [CX3001]  
MC9S08RC32MP  
MC9S08RC32VDW@SOIC28 [CX1033]  
MC9S08RC32VFD@QFN48 [CX4021]  
MC9S08RC32VFG@LQFP44 [CX3003]  
MC9S08RC32VFJ@LQFP32 [CX3001]  
MC9S08RC32VP  
MC9S08RC60CDW@SOIC28 [CX1033]  
MC9S08RC60CFD@QFN48 [CX4021]  
MC9S08RC60CFG@LQFP44 [CX3003]  
MC9S08RC60CFJ@LQFP32 [CX3001]  
MC9S08RC60CP  
MC9S08RC60MDW@SOIC28 [CX1033]  
MC9S08RC60MFD@QFN48 [CX4021]  
MC9S08RC60MFG@LQFP44 [CX3003]  
MC9S08RC60MFJ@LQFP32 [CX3001]  
MC9S08RC60MP  
MC9S08RC60VDW@SOIC28 [CX1033]  
MC9S08RC60VFD@QFN48 [CX4021]  
MC9S08RC60VFG@LQFP44 [CX3003]  
MC9S08RC60VFJ@LQFP32 [CX3001]  
MC9S08RC60VP  
MC9S08RC8CDW@SOIC28 [CX1033]

MC9S08QG8CFFE@QFN16 [CX4009]  
MC9S08QG8CFQE@DFN8 [CX4004]  
MC9S08QG8CPBE  
MC9S08QG8MDNE@SOIC8 [CX1030]  
MC9S08QG8MDTE@TSSOP16 [CX1000]  
MC9S08QG8MFFE@QFN16 [CX4009]  
MC9S08QG8MFQE@DFN8 [CX4004]  
MC9S08QG8MPBE  
MC9S08QG8VDNE@SOIC8 [CX1030]  
MC9S08QG8VDTE@TSSOP16 [CX1000]  
MC9S08QG8VFFE@QFN16 [CX4009]  
MC9S08QG8VFQE@DFN8 [CX4004]  
MC9S08QG8VPBE  
MC9S08RC16CDWE@SOIC28 [CX1033]  
MC9S08RC16CFDE@QFN48 [CX4021]  
MC9S08RC16CFGE@LQFP44 [CX3003]  
MC9S08RC16CFJE@LQFP32 [CX3001]  
MC9S08RC16CPE  
MC9S08RC16MDWE@SOIC28 [CX1033]  
MC9S08RC16MFDE@QFN48 [CX4021]  
MC9S08RC16MFG@LQFP44 [CX3003]  
MC9S08RC16MFJE@LQFP32 [CX3001]  
MC9S08RC16MPE  
MC9S08RC16VDWE@SOIC28 [CX1033]  
MC9S08RC16VFDE@QFN48 [CX4021]  
MC9S08RC16VFGE@LQFP44 [CX3003]  
MC9S08RC16VFJE@LQFP32 [CX3001]  
MC9S08RC16VPE  
MC9S08RC32CDWE@SOIC28 [CX1033]  
MC9S08RC32CFDE@QFN48 [CX4021]  
MC9S08RC32CFGE@LQFP44 [CX3003]  
MC9S08RC32CFJE@LQFP32 [CX3001]  
MC9S08RC32CPE  
MC9S08RC32MDWE@SOIC28 [CX1033]  
MC9S08RC32MFDE@QFN48 [CX4021]  
MC9S08RC32MFG@LQFP44 [CX3003]  
MC9S08RC32MFJE@LQFP32 [CX3001]  
MC9S08RC32MPE  
MC9S08RC32VDWE@SOIC28 [CX1033]  
MC9S08RC32VFDE@QFN48 [CX4021]  
MC9S08RC32VFGE@LQFP44 [CX3003]  
MC9S08RC32VFJE@LQFP32 [CX3001]  
MC9S08RC32VPE  
MC9S08RC60CDWE@SOIC28 [CX1033]  
MC9S08RC60CFDE@QFN48 [CX4021]  
MC9S08RC60CFGE@LQFP44 [CX3003]  
MC9S08RC60CFJE@LQFP32 [CX3001]  
MC9S08RC60CPE  
MC9S08RC60MDWE@SOIC28 [CX1033]  
MC9S08RC60MFDE@QFN48 [CX4021]  
MC9S08RC60MFG@LQFP44 [CX3003]  
MC9S08RC60MFJE@LQFP32 [CX3001]  
MC9S08RC60MPE  
MC9S08RC60VDWE@SOIC28 [CX1033]  
MC9S08RC60VFDE@QFN48 [CX4021]  
MC9S08RC60VFGE@LQFP44 [CX3003]  
MC9S08RC60VFJE@LQFP32 [CX3001]  
MC9S08RC60VPE  
MC9S08RC8CDWE@SOIC28 [CX1033]

MC9S08RC8CFD@QFN48 [CX4021]  
MC9S08RC8CFG@LQFP44 [CX3003]  
MC9S08RC8CFJ@LQFP32 [CX3001]  
MC9S08RC8CP  
MC9S08RC8MDW@SOIC28 [CX1033]  
MC9S08RC8MFD@QFN48 [CX4021]  
MC9S08RC8MFG@LQFP44 [CX3003]  
MC9S08RC8MFJ@LQFP32 [CX3001]  
MC9S08RC8MP  
MC9S08RC8VDW@SOIC28 [CX1033]  
MC9S08RC8VFD@QFN48 [CX4021]  
MC9S08RC8VFG@LQFP44 [CX3003]  
MC9S08RC8VFJ@LQFP32 [CX3001]  
MC9S08RC8VP  
MC9S08RD16CDW@SOIC28 [CX1033]  
MC9S08RD16CFD@QFN48 [CX4021]  
MC9S08RD16CFG@LQFP44 [CX3003]  
MC9S08RD16CFJ@LQFP32 [CX3001]  
MC9S08RD16CP  
MC9S08RD16MDW@SOIC28 [CX1033]  
MC9S08RD16MFD@QFN48 [CX4021]  
MC9S08RD16MFG@LQFP44 [CX3003]  
MC9S08RD16MFJ@LQFP32 [CX3001]  
MC9S08RD16MP  
MC9S08RD16VDW@SOIC28 [CX1033]  
MC9S08RD16VFD@QFN48 [CX4021]  
MC9S08RD16VFG@LQFP44 [CX3003]  
MC9S08RD16VFJ@LQFP32 [CX3001]  
MC9S08RD16VP  
MC9S08RD32CDW@SOIC28 [CX1033]  
MC9S08RD32CFD@QFN48 [CX4021]  
MC9S08RD32CFG@LQFP44 [CX3003]  
MC9S08RD32CFJ@LQFP32 [CX3001]  
MC9S08RD32CP  
MC9S08RD32MDW@SOIC28 [CX1033]  
MC9S08RD32MFD@QFN48 [CX4021]  
MC9S08RD32MFG@LQFP44 [CX3003]  
MC9S08RD32MFJ@LQFP32 [CX3001]  
MC9S08RD32MP  
MC9S08RD32VDW@SOIC28 [CX1033]  
MC9S08RD32VFD@QFN48 [CX4021]  
MC9S08RD32VFG@LQFP44 [CX3003]  
MC9S08RD32VFJ@LQFP32 [CX3001]  
MC9S08RD32VP  
MC9S08RD60CDW@SOIC28 [CX1033]  
MC9S08RD60CFD@QFN48 [CX4021]  
MC9S08RD60CFG@LQFP44 [CX3003]  
MC9S08RD60CFJ@LQFP32 [CX3001]  
MC9S08RD60CP  
MC9S08RD60MDW@SOIC28 [CX1033]  
MC9S08RD60MFD@QFN48 [CX4021]  
MC9S08RD60MFG@LQFP44 [CX3003]  
MC9S08RD60MFJ@LQFP32 [CX3001]  
MC9S08RD60MP  
MC9S08RD60VDW@SOIC28 [CX1033]  
MC9S08RD60VFD@QFN48 [CX4021]  
MC9S08RD60VFG@LQFP44 [CX3003]  
MC9S08RD60VFJ@LQFP32 [CX3001]  
MC9S08RD60VP

MC9S08RC8CFDE@QFN48 [CX4021]  
MC9S08RC8CFGE@LQFP44 [CX3003]  
MC9S08RC8CFJE@LQFP32 [CX3001]  
MC9S08RC8CPE  
MC9S08RC8MDWE@SOIC28 [CX1033]  
MC9S08RC8MFDE@QFN48 [CX4021]  
MC9S08RC8MFGE@LQFP44 [CX3003]  
MC9S08RC8MFJE@LQFP32 [CX3001]  
MC9S08RC8MPE  
MC9S08RC8VDWE@SOIC28 [CX1033]  
MC9S08RC8VFDE@QFN48 [CX4021]  
MC9S08RC8VFGE@LQFP44 [CX3003]  
MC9S08RC8VFJE@LQFP32 [CX3001]  
MC9S08RC8VPE  
MC9S08RD16CDWE@SOIC28 [CX1033]  
MC9S08RD16CFDE@QFN48 [CX4021]  
MC9S08RD16CFGE@LQFP44 [CX3003]  
MC9S08RD16CFJE@LQFP32 [CX3001]  
MC9S08RD16CPE  
MC9S08RD16MDWE@SOIC28 [CX1033]  
MC9S08RD16MFDE@QFN48 [CX4021]  
MC9S08RD16MFGE@LQFP44 [CX3003]  
MC9S08RD16MFJE@LQFP32 [CX3001]  
MC9S08RD16MPE  
MC9S08RD16VDWE@SOIC28 [CX1033]  
MC9S08RD16VFDE@QFN48 [CX4021]  
MC9S08RD16VFGE@LQFP44 [CX3003]  
MC9S08RD16VFJE@LQFP32 [CX3001]  
MC9S08RD16VPE  
MC9S08RD32CDWE@SOIC28 [CX1033]  
MC9S08RD32CFDE@QFN48 [CX4021]  
MC9S08RD32CFGE@LQFP44 [CX3003]  
MC9S08RD32CFJE@LQFP32 [CX3001]  
MC9S08RD32CPE  
MC9S08RD32MDWE@SOIC28 [CX1033]  
MC9S08RD32MFDE@QFN48 [CX4021]  
MC9S08RD32MFGE@LQFP44 [CX3003]  
MC9S08RD32MFJE@LQFP32 [CX3001]  
MC9S08RD32MPE  
MC9S08RD32VDWE@SOIC28 [CX1033]  
MC9S08RD32VFDE@QFN48 [CX4021]  
MC9S08RD32VFGE@LQFP44 [CX3003]  
MC9S08RD32VFJE@LQFP32 [CX3001]  
MC9S08RD32VPE  
MC9S08RD60CDWE@SOIC28 [CX1033]  
MC9S08RD60CFDE@QFN48 [CX4021]  
MC9S08RD60CFGE@LQFP44 [CX3003]  
MC9S08RD60CFJE@LQFP32 [CX3001]  
MC9S08RD60CPE  
MC9S08RD60MDWE@SOIC28 [CX1033]  
MC9S08RD60MFDE@QFN48 [CX4021]  
MC9S08RD60MFGE@LQFP44 [CX3003]  
MC9S08RD60MFJE@LQFP32 [CX3001]  
MC9S08RD60MPE  
MC9S08RD60VDWE@SOIC28 [CX1033]  
MC9S08RD60VFDE@QFN48 [CX4021]  
MC9S08RD60VFGE@LQFP44 [CX3003]  
MC9S08RD60VFJE@LQFP32 [CX3001]  
MC9S08RD60VPE

MC9S08RD8CDW@SOIC28 [CX1033]  
MC9S08RD8CFD@QFN48 [CX4021]  
MC9S08RD8CFG@LQFP44 [CX3003]  
MC9S08RD8CFJ@LQFP32 [CX3001]  
MC9S08RD8CP  
MC9S08RD8MDW@SOIC28 [CX1033]  
MC9S08RD8MFD@QFN48 [CX4021]  
MC9S08RD8MFG@LQFP44 [CX3003]  
MC9S08RD8MFJ@LQFP32 [CX3001]  
MC9S08RD8MP  
MC9S08RD8VDW@SOIC28 [CX1033]  
MC9S08RD8VFD@QFN48 [CX4021]  
MC9S08RD8VFG@LQFP44 [CX3003]  
MC9S08RD8VFJ@LQFP32 [CX3001]  
MC9S08RD8VP  
MC9S08RE16CDW@SOIC28 [CX1033]  
MC9S08RE16CFD@QFN48 [CX4021]  
MC9S08RE16CFG@LQFP44 [CX3003]  
MC9S08RE16CFJ@LQFP32 [CX3001]  
MC9S08RE16CP  
MC9S08RE16MDW@SOIC28 [CX1033]  
MC9S08RE16MFD@QFN48 [CX4021]  
MC9S08RE16MFG@LQFP44 [CX3003]  
MC9S08RE16MFJ@LQFP32 [CX3001]  
MC9S08RE16MP  
MC9S08RE16VDW@SOIC28 [CX1033]  
MC9S08RE16VFD@QFN48 [CX4021]  
MC9S08RE16VFG@LQFP44 [CX3003]  
MC9S08RE16VFJ@LQFP32 [CX3001]  
MC9S08RE16VP  
MC9S08RE32CDW@SOIC28 [CX1033]  
MC9S08RE32CFD@QFN48 [CX4021]  
MC9S08RE32CFG@LQFP44 [CX3003]  
MC9S08RE32CFJ@LQFP32 [CX3001]  
MC9S08RE32CP  
MC9S08RE32MDW@SOIC28 [CX1033]  
MC9S08RE32MFD@QFN48 [CX4021]  
MC9S08RE32MFG@LQFP44 [CX3003]  
MC9S08RE32MFJ@LQFP32 [CX3001]  
MC9S08RE32MP  
MC9S08RE32VDW@SOIC28 [CX1033]  
MC9S08RE32VFD@QFN48 [CX4021]  
MC9S08RE32VFG@LQFP44 [CX3003]  
MC9S08RE32VFJ@LQFP32 [CX3001]  
MC9S08RE32VP  
MC9S08RE60CDW@SOIC28 [CX1033]  
MC9S08RE60CFD@QFN48 [CX4021]  
MC9S08RE60CFG@LQFP44 [CX3003]  
MC9S08RE60CFJ@LQFP32 [CX3001]  
MC9S08RE60CP  
MC9S08RE60MDW@SOIC28 [CX1033]  
MC9S08RE60MFD@QFN48 [CX4021]  
MC9S08RE60MFG@LQFP44 [CX3003]  
MC9S08RE60MFJ@LQFP32 [CX3001]  
MC9S08RE60MP  
MC9S08RE60VDW@SOIC28 [CX1033]  
MC9S08RE60VFD@QFN48 [CX4021]  
MC9S08RE60VFG@LQFP44 [CX3003]  
MC9S08RE60VFJ@LQFP32 [CX3001]

MC9S08RD8CDWE@SOIC28 [CX1033]  
MC9S08RD8CFDE@QFN48 [CX4021]  
MC9S08RD8CFGE@LQFP44 [CX3003]  
MC9S08RD8CFJE@LQFP32 [CX3001]  
MC9S08RD8CPE  
MC9S08RD8MDWE@SOIC28 [CX1033]  
MC9S08RD8MFDE@QFN48 [CX4021]  
MC9S08RD8MFGE@LQFP44 [CX3003]  
MC9S08RD8MFJE@LQFP32 [CX3001]  
MC9S08RD8MPE  
MC9S08RD8VDWE@SOIC28 [CX1033]  
MC9S08RD8VFDE@QFN48 [CX4021]  
MC9S08RD8VFGE@LQFP44 [CX3003]  
MC9S08RD8VFJE@LQFP32 [CX3001]  
MC9S08RD8VPE  
MC9S08RE16CDWE@SOIC28 [CX1033]  
MC9S08RE16CFDE@QFN48 [CX4021]  
MC9S08RE16CFGE@LQFP44 [CX3003]  
MC9S08RE16CFJE@LQFP32 [CX3001]  
MC9S08RE16CPE  
MC9S08RE16MDWE@SOIC28 [CX1033]  
MC9S08RE16MFDE@QFN48 [CX4021]  
MC9S08RE16MFGE@LQFP44 [CX3003]  
MC9S08RE16MFJE@LQFP32 [CX3001]  
MC9S08RE16MPE  
MC9S08RE16VDWE@SOIC28 [CX1033]  
MC9S08RE16VFDE@QFN48 [CX4021]  
MC9S08RE16VFGE@LQFP44 [CX3003]  
MC9S08RE16VFJE@LQFP32 [CX3001]  
MC9S08RE16VPE  
MC9S08RE32CDWE@SOIC28 [CX1033]  
MC9S08RE32CFDE@QFN48 [CX4021]  
MC9S08RE32CFGE@LQFP44 [CX3003]  
MC9S08RE32CFJE@LQFP32 [CX3001]  
MC9S08RE32CPE  
MC9S08RE32MDWE@SOIC28 [CX1033]  
MC9S08RE32MFDE@QFN48 [CX4021]  
MC9S08RE32MFGE@LQFP44 [CX3003]  
MC9S08RE32MFJE@LQFP32 [CX3001]  
MC9S08RE32MPE  
MC9S08RE32VDWE@SOIC28 [CX1033]  
MC9S08RE32VFDE@QFN48 [CX4021]  
MC9S08RE32VFGE@LQFP44 [CX3003]  
MC9S08RE32VFJE@LQFP32 [CX3001]  
MC9S08RE32VPE  
MC9S08RE60CDWE@SOIC28 [CX1033]  
MC9S08RE60CFDE@QFN48 [CX4021]  
MC9S08RE60CFGE@LQFP44 [CX3003]  
MC9S08RE60CFJE@LQFP32 [CX3001]  
MC9S08RE60CPE  
MC9S08RE60MDWE@SOIC28 [CX1033]  
MC9S08RE60MFDE@QFN48 [CX4021]  
MC9S08RE60MFGE@LQFP44 [CX3003]  
MC9S08RE60MFJE@LQFP32 [CX3001]  
MC9S08RE60MPE  
MC9S08RE60VDWE@SOIC28 [CX1033]  
MC9S08RE60VFDE@QFN48 [CX4021]  
MC9S08RE60VFGE@LQFP44 [CX3003]  
MC9S08RE60VFJE@LQFP32 [CX3001]



MC9S08RE60VP  
MC9S08RE8CDW@SOIC28 [CX1033]  
MC9S08RE8CFD@QFN48 [CX4021]  
MC9S08RE8CFG@LQFP44 [CX3003]  
MC9S08RE8CFJ@LQFP32 [CX3001]  
MC9S08RE8CP  
MC9S08RE8MDW@SOIC28 [CX1033]  
MC9S08RE8MFD@QFN48 [CX4021]  
MC9S08RE8MFG@LQFP44 [CX3003]  
MC9S08RE8MFJ@LQFP32 [CX3001]  
MC9S08RE8MP  
MC9S08RE8VDW@SOIC28 [CX1033]  
MC9S08RE8VFD@QFN48 [CX4021]  
MC9S08RE8VFG@LQFP44 [CX3003]  
MC9S08RE8VFJ@LQFP32 [CX3001]  
MC9S08RE8VP  
MC9S08RG16CDW@SOIC28 [CX1033]  
MC9S08RG16CFD@QFN48 [CX4021]  
MC9S08RG16CFG@LQFP44 [CX3003]  
MC9S08RG16CFJ@LQFP32 [CX3001]  
MC9S08RG16CP  
MC9S08RG16MDW@SOIC28 [CX1033]  
MC9S08RG16MFD@QFN48 [CX4021]  
MC9S08RG16MFG@LQFP44 [CX3003]  
MC9S08RG16MFJ@LQFP32 [CX3001]  
MC9S08RG16MP  
MC9S08RG16VDW@SOIC28 [CX1033]  
MC9S08RG16VFD@QFN48 [CX4021]  
MC9S08RG16VFG@LQFP44 [CX3003]  
MC9S08RG16VFJ@LQFP32 [CX3001]  
MC9S08RG16VP  
MC9S08RG32CDW@SOIC28 [CX1033]  
MC9S08RG32CFD@QFN48 [CX4021]  
MC9S08RG32CFG@LQFP44 [CX3003]  
MC9S08RG32CFJ@LQFP32 [CX3001]  
MC9S08RG32CP  
MC9S08RG32MDW@SOIC28 [CX1033]  
MC9S08RG32MFD@QFN48 [CX4021]  
MC9S08RG32MFG@LQFP44 [CX3003]  
MC9S08RG32MFJ@LQFP32 [CX3001]  
MC9S08RG32MP  
MC9S08RG32VDW@SOIC28 [CX1033]  
MC9S08RG32VFD@QFN48 [CX4021]  
MC9S08RG32VFG@LQFP44 [CX3003]  
MC9S08RG32VFJ@LQFP32 [CX3001]  
MC9S08RG32VP  
MC9S08RG60CDW@SOIC28 [CX1033]  
MC9S08RG60CFD@QFN48 [CX4021]  
MC9S08RG60CFG@LQFP44 [CX3003]  
MC9S08RG60CFJ@LQFP32 [CX3001]  
MC9S08RG60CP  
MC9S08RG60MDW@SOIC28 [CX1033]  
MC9S08RG60MFD@QFN48 [CX4021]  
MC9S08RG60MFG@LQFP44 [CX3003]  
MC9S08RG60MFJ@LQFP32 [CX3001]  
MC9S08RG60MP  
MC9S08RG60VDW@SOIC28 [CX1033]  
MC9S08RG60VFD@QFN48 [CX4021]  
MC9S08RG60VFG@LQFP44 [CX3003]

MC9S08RE60VPE  
MC9S08RE8CDWE@SOIC28 [CX1033]  
MC9S08RE8CFDE@QFN48 [CX4021]  
MC9S08RE8CFGE@LQFP44 [CX3003]  
MC9S08RE8CFJE@LQFP32 [CX3001]  
MC9S08RE8CPE  
MC9S08RE8MDWE@SOIC28 [CX1033]  
MC9S08RE8MFDE@QFN48 [CX4021]  
MC9S08RE8MFGE@LQFP44 [CX3003]  
MC9S08RE8MFJE@LQFP32 [CX3001]  
MC9S08RE8MPE  
MC9S08RE8VDWE@SOIC28 [CX1033]  
MC9S08RE8VFDE@QFN48 [CX4021]  
MC9S08RE8VFGE@LQFP44 [CX3003]  
MC9S08RE8VFJE@LQFP32 [CX3001]  
MC9S08RE8VPE  
MC9S08RG16CDWE@SOIC28 [CX1033]  
MC9S08RG16CFDE@QFN48 [CX4021]  
MC9S08RG16CFGE@LQFP44 [CX3003]  
MC9S08RG16CFJE@LQFP32 [CX3001]  
MC9S08RG16CPE  
MC9S08RG16MDWE@SOIC28 [CX1033]  
MC9S08RG16MFDE@QFN48 [CX4021]  
MC9S08RG16MFGE@LQFP44 [CX3003]  
MC9S08RG16MFJE@LQFP32 [CX3001]  
MC9S08RG16MPE  
MC9S08RG16VDWE@SOIC28 [CX1033]  
MC9S08RG16VFDE@QFN48 [CX4021]  
MC9S08RG16VFGE@LQFP44 [CX3003]  
MC9S08RG16VFJE@LQFP32 [CX3001]  
MC9S08RG16VPE  
MC9S08RG32CDWE@SOIC28 [CX1033]  
MC9S08RG32CFDE@QFN48 [CX4021]  
MC9S08RG32CFGE@LQFP44 [CX3003]  
MC9S08RG32CFJE@LQFP32 [CX3001]  
MC9S08RG32CPE  
MC9S08RG32MDWE@SOIC28 [CX1033]  
MC9S08RG32MFDE@QFN48 [CX4021]  
MC9S08RG32MFGE@LQFP44 [CX3003]  
MC9S08RG32MFJE@LQFP32 [CX3001]  
MC9S08RG32MPE  
MC9S08RG32VDWE@SOIC28 [CX1033]  
MC9S08RG32VFDE@QFN48 [CX4021]  
MC9S08RG32VFGE@LQFP44 [CX3003]  
MC9S08RG32VFJE@LQFP32 [CX3001]  
MC9S08RG32VPE  
MC9S08RG60CDWE@SOIC28 [CX1033]  
MC9S08RG60CFDE@QFN48 [CX4021]  
MC9S08RG60CFGE@LQFP44 [CX3003]  
MC9S08RG60CFJE@LQFP32 [CX3001]  
MC9S08RG60CPE  
MC9S08RG60MDWE@SOIC28 [CX1033]  
MC9S08RG60MFDE@QFN48 [CX4021]  
MC9S08RG60MFGE@LQFP44 [CX3003]  
MC9S08RG60MFJE@LQFP32 [CX3001]  
MC9S08RG60MPE  
MC9S08RG60VDWE@SOIC28 [CX1033]  
MC9S08RG60VFDE@QFN48 [CX4021]  
MC9S08RG60VFGE@LQFP44 [CX3003]

MC9S08RG60VFJ@LQFP32 [CX3001]  
MC9S08RG60VP  
MC9S08RG8CDW@SOIC28 [CX1033]  
MC9S08RG8CFD@QFN48 [CX4021]  
MC9S08RG8CFG@LQFP44 [CX3003]  
MC9S08RG8CFJ@LQFP32 [CX3001]  
MC9S08RG8CP  
MC9S08RG8MDW@SOIC28 [CX1033]  
MC9S08RG8MFD@QFN48 [CX4021]  
MC9S08RG8MFG@LQFP44 [CX3003]  
MC9S08RG8MFJ@LQFP32 [CX3001]  
MC9S08RG8MP  
MC9S08RG8VDW@SOIC28 [CX1033]  
MC9S08RG8VFD@QFN48 [CX4021]  
MC9S08RG8VFG@LQFP44 [CX3003]  
MC9S08RG8VFJ@LQFP32 [CX3001]  
MC9S08RG8VP  
MC9S08SE4CRL [CX0001]  
MC9S08SE4CWL [CX1033]  
MC9S08SE4MTG [CX1001]  
MC9S08SE4VRL [CX0001]  
MC9S08SE4VWL [CX1033]  
MC9S08SE8CTG [CX1001]  
MC9S08SE8MRL [CX0001]  
MC9S08SE8MWL [CX1033]  
MC9S08SE8VTG [CX1001]  
MC9S08SG16CTG@TSSOP16 [CX1000]  
MC9S08SG16CTJ@TSSOP20 [CX1000]  
MC9S08SG16CTL@TSSOP28 [CX1001]  
MC9S08SG16MTG@TSSOP16 [CX1000]  
MC9S08SG16MTJ@TSSOP20 [CX1000]  
MC9S08SG16MTL@TSSOP28 [CX1001]  
MC9S08SG16VTG@TSSOP16 [CX1000]  
MC9S08SG16VTJ@TSSOP20 [CX1000]  
MC9S08SG16VTL@TSSOP28 [CX1001]  
MC9S08SG32CTG@TSSOP16 [CX1000]  
MC9S08SG32CTJ@TSSOP20 [CX1000]  
MC9S08SG32CTL@TSSOP28 [CX1001]  
MC9S08SG32MTG@TSSOP16 [CX1000]  
MC9S08SG32MTJ@TSSOP20 [CX1000]  
MC9S08SG32MTL@TSSOP28 [CX1001]  
MC9S08SG32VTG@TSSOP16 [CX1000]  
MC9S08SG32VTJ@TSSOP20 [CX1000]  
MC9S08SG32VTL@TSSOP28 [CX1001]  
MC9S08SG4CSC@SOIC8 [CX1030]  
MC9S08SG4CTG@TSSOP16 [CX1000]  
MC9S08SG4CTJ@TSSOP20 [CX1000]  
MC9S08SG4MSC@SOIC8 [CX1030]  
MC9S08SG4MTG@TSSOP16 [CX1000]  
MC9S08SG4MTJ@TSSOP20 [CX1000]  
MC9S08SG4VSC@SOIC8 [CX1030]  
MC9S08SG4VTG@TSSOP16 [CX1000]  
MC9S08SG4VTJ@TSSOP20 [CX1000]  
MC9S08SG8CSC@SOIC8 [CX1030]  
MC9S08SG8CTG@TSSOP16 [CX1000]  
MC9S08SG8CTJ@TSSOP20 [CX1000]  
MC9S08SG8MSC@SOIC8 [CX1030]  
MC9S08SG8MTG@TSSOP16 [CX1000]  
MC9S08SG8MTJ@TSSOP20 [CX1000]

MC9S08RG60VFJE@LQFP32 [CX3001]  
MC9S08RG60VPE  
MC9S08RG8CDWE@SOIC28 [CX1033]  
MC9S08RG8CFDE@QFN48 [CX4021]  
MC9S08RG8CFGE@LQFP44 [CX3003]  
MC9S08RG8CFJE@LQFP32 [CX3001]  
MC9S08RG8CPE  
MC9S08RG8MDWE@SOIC28 [CX1033]  
MC9S08RG8MFDE@QFN48 [CX4021]  
MC9S08RG8MFGE@LQFP44 [CX3003]  
MC9S08RG8MFJE@LQFP32 [CX3001]  
MC9S08RG8MPPE  
MC9S08RG8VDWE@SOIC28 [CX1033]  
MC9S08RG8VFDE@QFN48 [CX4021]  
MC9S08RG8VFGE@LQFP44 [CX3003]  
MC9S08RG8VFJE@LQFP32 [CX3001]  
MC9S08RG8VPE  
MC9S08SE4CTG [CX1001]  
MC9S08SE4MRL [CX0001]  
MC9S08SE4MWL [CX1033]  
MC9S08SE4VTG [CX1001]  
MC9S08SE8CRL [CX0001]  
MC9S08SE8CWL [CX1033]  
MC9S08SE8MTG [CX1001]  
MC9S08SE8VRL [CX0001]  
MC9S08SE8VWL [CX1033]  
MC9S08SG16CTGE@TSSOP16 [CX1000]  
MC9S08SG16CTJE@TSSOP20 [CX1000]  
MC9S08SG16CTLE@TSSOP28 [CX1001]  
MC9S08SG16MTGE@TSSOP16 [CX1000]  
MC9S08SG16MTJE@TSSOP20 [CX1000]  
MC9S08SG16MTLE@TSSOP28 [CX1001]  
MC9S08SG16VTGE@TSSOP16 [CX1000]  
MC9S08SG16VTJE@TSSOP20 [CX1000]  
MC9S08SG16VTLE@TSSOP28 [CX1001]  
MC9S08SG32CTGE@TSSOP16 [CX1000]  
MC9S08SG32CTJE@TSSOP20 [CX1000]  
MC9S08SG32CTLE@TSSOP28 [CX1001]  
MC9S08SG32MTGE@TSSOP16 [CX1000]  
MC9S08SG32MTJE@TSSOP20 [CX1000]  
MC9S08SG32MTLE@TSSOP28 [CX1001]  
MC9S08SG32VTGE@TSSOP16 [CX1000]  
MC9S08SG32VTJE@TSSOP20 [CX1000]  
MC9S08SG32VTLE@TSSOP28 [CX1001]  
MC9S08SG4CSCE@SOIC8 [CX1030]  
MC9S08SG4CTGE@TSSOP16 [CX1000]  
MC9S08SG4CTJE@TSSOP20 [CX1000]  
MC9S08SG4MSCE@SOIC8 [CX1030]  
MC9S08SG4MTGE@TSSOP16 [CX1000]  
MC9S08SG4MTJE@TSSOP20 [CX1000]  
MC9S08SG4VSCE@SOIC8 [CX1030]  
MC9S08SG4VTGE@TSSOP16 [CX1000]  
MC9S08SG4VTJE@TSSOP20 [CX1000]  
MC9S08SG8CSCE@SOIC8 [CX1030]  
MC9S08SG8CTGE@TSSOP16 [CX1000]  
MC9S08SG8CTJE@TSSOP20 [CX1000]  
MC9S08SG8MSCE@SOIC8 [CX1030]  
MC9S08SG8MTGE@TSSOP16 [CX1000]  
MC9S08SG8MTJE@TSSOP20 [CX1000]

MC9S08SG8VSC@SOIC8 [CX1030]                   MC9S08SG8VSCE@SOIC8 [CX1030]  
MC9S08SG8VTG@TSSOP16 [CX1000]               MC9S08SG8VTGE@TSSOP16 [CX1000]  
MC9S08SG8VTJ@TSSOP20 [CX1000]               MC9S08SG8VTJE@TSSOP20 [CX1000]  
MC9S08SH16CTG@TSSOP16 [CX1000]               MC9S08SH16CTGE@TSSOP16 [CX1000]  
MC9S08SH16CTJ@TSSOP20 [CX1000]               MC9S08SH16CTJE@TSSOP20 [CX1000]  
MC9S08SH16CTL@TSSOP28 [CX1001]               MC9S08SH16CTLE@TSSOP28 [CX1001]  
MC9S08SH16CWL@SOIC28 [CX1033]                MC9S08SH16CWLE@SOIC28 [CX1033]  
MC9S08SH16MTG@TSSOP16 [CX1000]               MC9S08SH16MTGE@TSSOP16 [CX1000]  
MC9S08SH16MTJ@TSSOP20 [CX1000]               MC9S08SH16MTJE@TSSOP20 [CX1000]  
MC9S08SH16MTL@TSSOP28 [CX1001]               MC9S08SH16MTLE@TSSOP28 [CX1001]  
MC9S08SH16MWL@SOIC28 [CX1033]                MC9S08SH16MWLE@SOIC28 [CX1033]  
MC9S08SH16VTG@TSSOP16 [CX1000]               MC9S08SH16VTGE@TSSOP16 [CX1000]  
MC9S08SH16VTJ@TSSOP20 [CX1000]               MC9S08SH16VTJE@TSSOP20 [CX1000]  
MC9S08SH16VTL@TSSOP28 [CX1001]               MC9S08SH16VTLE@TSSOP28 [CX1001]  
MC9S08SH16VWL@SOIC28 [CX1033]                MC9S08SH16VWLE@SOIC28 [CX1033]  
MC9S08SH32CTG@TSSOP16 [CX1000]               MC9S08SH32CTGE@TSSOP16 [CX1000]  
MC9S08SH32CTJ@TSSOP20 [CX1000]               MC9S08SH32CTJE@TSSOP20 [CX1000]  
MC9S08SH32CTL@TSSOP28 [CX1001]               MC9S08SH32CTLE@TSSOP28 [CX1001]  
MC9S08SH32CWL@SOIC28 [CX1033]                MC9S08SH32CWLE@SOIC28 [CX1033]  
MC9S08SH32MTG@TSSOP16 [CX1000]               MC9S08SH32MTGE@TSSOP16 [CX1000]  
MC9S08SH32MTJ@TSSOP20 [CX1000]               MC9S08SH32MTJE@TSSOP20 [CX1000]  
MC9S08SH32MTL@TSSOP28 [CX1001]               MC9S08SH32MTLE@TSSOP28 [CX1001]  
MC9S08SH32MWL@SOIC28 [CX1033]                MC9S08SH32MWLE@SOIC28 [CX1033]  
MC9S08SH32VTG@TSSOP16 [CX1000]               MC9S08SH32VTGE@TSSOP16 [CX1000]  
MC9S08SH32VTJ@TSSOP20 [CX1000]               MC9S08SH32VTJE@TSSOP20 [CX1000]  
MC9S08SH32VTL@TSSOP28 [CX1001]               MC9S08SH32VTLE@TSSOP28 [CX1001]  
MC9S08SH32VWL@SOIC28 [CX1033]                MC9S08SH32VWLE@SOIC28 [CX1033]  
MC9S08SH4CFK@QFN24 [CX4012]  
MC9S08SH4CFK@QFN24(auto trim) [CX4012]  
MC9S08SH4CFKE@QFN24 [CX4012]  
MC9S08SH4CFKE@QFN24(auto trim) [CX4012]  
MC9S08SH4CPJ                                    MC9S08SH4CPJ(auto trim)  
MC9S08SH4CPJE                                  MC9S08SH4CPJE(auto trim)  
MC9S08SH4CSC@SOIC8 [CX1030]  
MC9S08SH4CSC@SOIC8(auto trim) [CX1030]  
MC9S08SH4CSCE@SOIC8 [CX1030]  
MC9S08SH4CSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH4CTG@TSSOP16 [CX1000]  
MC9S08SH4CTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH4CTGE@TSSOP16 [CX1000]  
MC9S08SH4CTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH4CTJ@TSSOP20 [CX1000]  
MC9S08SH4CTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH4CTJE@TSSOP20 [CX1000]  
MC9S08SH4CTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH4CWJ@SOIC20 [CX1033]  
MC9S08SH4CWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH4CWJE@SOIC20 [CX1033]  
MC9S08SH4CWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH4MFK@QFN24 [CX4012]  
MC9S08SH4MFK@QFN24(auto trim) [CX4012]  
MC9S08SH4MFKE@QFN24 [CX4012]  
MC9S08SH4MFKE@QFN24(auto trim) [CX4012]  
MC9S08SH4MPJ                                    MC9S08SH4MPJ(auto trim)  
MC9S08SH4MPJE                                  MC9S08SH4MPJE(auto trim)  
MC9S08SH4MSC@SOIC8 [CX1030]  
MC9S08SH4MSC@SOIC8(auto trim) [CX1030]  
MC9S08SH4MSCE@SOIC8 [CX1030]  
MC9S08SH4MSCE@SOIC8(auto trim) [CX1030]

MC9S08SH4MTG@TSSOP16 [CX1000]  
MC9S08SH4MTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH4MTGE@TSSOP16 [CX1000]  
MC9S08SH4MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH4MTJ@TSSOP20 [CX1000]  
MC9S08SH4MTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH4MTJE@TSSOP20 [CX1000]  
MC9S08SH4MTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH4MWJ@SOIC20 [CX1033]  
MC9S08SH4MWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH4MWJE@SOIC20 [CX1033]  
MC9S08SH4MWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH4VFK@QFN24 [CX4012]  
MC9S08SH4VFK@QFN24(auto trim) [CX4012]  
MC9S08SH4VFKE@QFN24 [CX4012]  
MC9S08SH4VFKE@QFN24(auto trim) [CX4012]  
MC9S08SH4VPJ MC9S08SH4VPJ(auto trim)  
MC9S08SH4VPJE MC9S08SH4VPJE(auto trim)  
MC9S08SH4VSC@SOIC8 [CX1030]  
MC9S08SH4VSC@SOIC8(auto trim) [CX1030]  
MC9S08SH4VSCE@SOIC8 [CX1030]  
MC9S08SH4VSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH4VTG@TSSOP16 [CX1000]  
MC9S08SH4VTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH4VTGE@TSSOP16 [CX1000]  
MC9S08SH4VTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH4VTJ@TSSOP20 [CX1000]  
MC9S08SH4VTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH4VTJE@TSSOP20 [CX1000]  
MC9S08SH4VTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH4VWJ@SOIC20 [CX1033]  
MC9S08SH4VWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH4VWJE@SOIC20 [CX1033]  
MC9S08SH4VWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH8CFK@QFN24 [CX4012]  
MC9S08SH8CFK@QFN24(auto trim) [CX4012]  
MC9S08SH8CFKE@QFN24 [CX4012]  
MC9S08SH8CFKE@QFN24(auto trim) [CX4012]  
MC9S08SH8CPJ MC9S08SH8CPJ(auto trim)  
MC9S08SH8CPJE MC9S08SH8CPJE(auto trim)  
MC9S08SH8CSC@SOIC8 [CX1030]  
MC9S08SH8CSC@SOIC8(auto trim) [CX1030]  
MC9S08SH8CSCE@SOIC8 [CX1030]  
MC9S08SH8CSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH8CTG@TSSOP16 [CX1000]  
MC9S08SH8CTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH8CTGE@TSSOP16 [CX1000]  
MC9S08SH8CTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH8CTJ@TSSOP20 [CX1000]  
MC9S08SH8CTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH8CTJE@TSSOP20 [CX1000]  
MC9S08SH8CTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH8CWJ@SOIC20 [CX1033]  
MC9S08SH8CWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH8CWJE@SOIC20 [CX1033]  
MC9S08SH8CWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH8MFK@QFN24 [CX4012]  
MC9S08SH8MFK@QFN24(auto trim) [CX4012]  
MC9S08SH8MFKE@QFN24 [CX4012]

MC9S08SH8MFKE@QFN24(auto trim) [CX4012]  
MC9S08SH8MPJ MC9S08SH8MPJ(auto trim)  
MC9S08SH8MPJE MC9S08SH8MPJE(auto trim)  
MC9S08SH8MSC@SOIC8 [CX1030]  
MC9S08SH8MSC@SOIC8(auto trim) [CX1030]  
MC9S08SH8MSCE@SOIC8 [CX1030]  
MC9S08SH8MSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH8MTG@TSSOP16 [CX1000]  
MC9S08SH8MTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH8MTGE@TSSOP16 [CX1000]  
MC9S08SH8MTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH8MTJ@TSSOP20 [CX1000]  
MC9S08SH8MTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH8MTJE@TSSOP20 [CX1000]  
MC9S08SH8MTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH8MWJ@SOIC20 [CX1033] MC9S08SH8MWJE@SOIC20 [CX1033]  
MC9S08SH8MWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH8VFK@QFN24 [CX4012]  
MC9S08SH8VFK@QFN24(auto trim) [CX4012]  
MC9S08SH8VFKE@QFN24 [CX4012]  
MC9S08SH8VFKE@QFN24(auto trim) [CX4012]  
MC9S08SH8VPJ MC9S08SH8VPJ(auto trim)  
MC9S08SH8VPJE MC9S08SH8VPJE(auto trim)  
MC9S08SH8VSC@SOIC8 [CX1030]  
MC9S08SH8VSC@SOIC8(auto trim) [CX1030]  
MC9S08SH8VSCE@SOIC8 [CX1030]  
MC9S08SH8VSCE@SOIC8(auto trim) [CX1030]  
MC9S08SH8VTG@TSSOP16 [CX1000]  
MC9S08SH8VTG@TSSOP16(auto trim) [CX1000]  
MC9S08SH8VTGE@TSSOP16 [CX1000]  
MC9S08SH8VTGE@TSSOP16(auto trim) [CX1000]  
MC9S08SH8VTJ@TSSOP20 [CX1000]  
MC9S08SH8VTJ@TSSOP20(auto trim) [CX1000]  
MC9S08SH8VTJE@TSSOP20 [CX1000]  
MC9S08SH8VTJE@TSSOP20(auto trim) [CX1000]  
MC9S08SH8VWJ@SOIC20 [CX1033]  
MC9S08SH8VWJ@SOIC20(auto trim) [CX1033]  
MC9S08SH8VWJE@SOIC20 [CX1033]  
MC9S08SH8VWJE@SOIC20(auto trim) [CX1033]  
MC9S08SH9MWJ@SOIC20(auto trim) [CX1033]  
MC9S08SL16CTJ@TSSOP20 [CX1000] MC9S08SL16CTJE@TSSOP20 [CX1000]  
MC9S08SL16CTL@TSSOP28 [CX1001] MC9S08SL16CTLE@TSSOP28 [CX1001]  
MC9S08SL16MTJ@TSSOP20 [CX1000] MC9S08SL16MTJE@TSSOP20 [CX1000]  
MC9S08SL16MTL@TSSOP28 [CX1001] MC9S08SL16MTLE@TSSOP28 [CX1001]  
MC9S08SL16VTJ@TSSOP20 [CX1000] MC9S08SL16VTJE@TSSOP20 [CX1000]  
MC9S08SL16VTL@TSSOP28 [CX1001] MC9S08SL16VTLE@TSSOP28 [CX1001]  
MC9S08SL8CTJ@TSSOP20 [CX1000] MC9S08SL8CTJE@TSSOP20 [CX1000]  
MC9S08SL8CTL@TSSOP28 [CX1001] MC9S08SL8CTLE@TSSOP28 [CX1001]  
MC9S08SL8MTJ@TSSOP20 [CX1000] MC9S08SL8MTJE@TSSOP20 [CX1000]  
MC9S08SL8MTL@TSSOP28 [CX1001] MC9S08SL8MTLE@TSSOP28 [CX1001]  
MC9S08SL8VTJ@TSSOP20 [CX1000] MC9S08SL8VTJE@TSSOP20 [CX1000]  
MC9S08SL8VTL@TSSOP28 [CX1001] MC9S08SL8VTLE@TSSOP28 [CX1001]  
MC9S08SV16CBM@SDIP32 [CX0032] MC9S08SV16CLC@LQFP32 [CX3001]  
MC9S08SV16MBM@SDIP32 [CX0032] MC9S08SV16MLC@LQFP32 [CX3001]  
MC9S08SV16VBM@SDIP32 [CX0032] MC9S08SV16VLC@LQFP32 [CX3001]  
MC9S08SV8CBM@SDIP32 [CX0032] MC9S08SV8CLC@LQFP32 [CX3001]  
MC9S08SV8MBM@SDIP32 [CX0032] MC9S08SV8MLC@LQFP32 [CX3001]  
MC9S08SV8VBM@SDIP32 [CX0032] MC9S08SV8VLC@LQFP32 [CX3001]  
MC9S12A128BCFU@TQFP80 [CX3018] MC9S12A128BMFU@TQFP80 [CX3018]

MC9S12A128BVFU@TQFP80 [CX3018]      MC9S12A128CFU@TQFP80 [CX3018]  
MC9S12A128MFU@TQFP80 [CX3018]      MC9S12A128VFU@TQFP80 [CX3018]  
MC9S12A256BCFU@TQFP80 [CX3018]      MC9S12A256BMFU@TQFP80 [CX3018]  
MC9S12A256BVFU@TQFP80 [CX3018]      MC9S12A256CFU@TQFP80 [CX3018]  
MC9S12A256MFU@TQFP80 [CX3018]      MC9S12A256VFU@TQFP80 [CX3018]  
MC9S12A64CFU@TQFP80 [CX3018]      MC9S12A64MFU@TQFP80 [CX3018]  
MC9S12A64VFU@TQFP80 [CX3018]      MC9S12B128CFU@TQFP80 [CX3018]  
MC9S12B128MFU@TQFP80 [CX3018]      MC9S12B128VFU@TQFP80 [CX3018]  
MC9S12B256CFU@TQFP80 [CX3018]      MC9S12B256MFU@TQFP80 [CX3018]  
MC9S12B256VFU@TQFP80 [CX3018]      MC9S12B64CFU@TQFP80 [CX3018]  
MC9S12B64MFU@TQFP80 [CX3018]      MC9S12B64VFU@TQFP80 [CX3018]  
MC9S12C128CFA@TQFP48 [CX3007]      MC9S12C128CFU@TQFP80 [CX3018]  
MC9S12C128CPB@TQFP52 [CX3010]      MC9S12C128MFA@TQFP48 [CX3007]  
MC9S12C128MFU@TQFP80 [CX3018]      MC9S12C128MPB@TQFP52 [CX3010]  
MC9S12C128VFA@TQFP48 [CX3007]      MC9S12C128VFU@TQFP80 [CX3018]  
MC9S12C128VPB@TQFP52 [CX3010]      MC9S12C32CFA16@TQFP48 [CX3007]  
MC9S12C32CFA25@TQFP48 [CX3007]      MC9S12C32CFU16@TQFP80 [CX3018]  
MC9S12C32CFU25@TQFP80 [CX3018]      MC9S12C32CPB16@TQFP52 [CX3010]  
MC9S12C32CPB25@TQFP52 [CX3010]      MC9S12C32MFA16@TQFP48 [CX3007]  
MC9S12C32MFA25@TQFP48 [CX3007]      MC9S12C32MFU16@TQFP80 [CX3018]  
MC9S12C32MFU25@TQFP80 [CX3018]      MC9S12C32MPB16@TQFP52 [CX3010]  
MC9S12C32MPB25@TQFP52 [CX3010]      MC9S12C32VFA16@TQFP48 [CX3007]  
MC9S12C32VFA25@TQFP48 [CX3007]      MC9S12C32VFU16@TQFP80 [CX3018]  
MC9S12C32VFU25@TQFP80 [CX3018]      MC9S12C32VPB16@TQFP52 [CX3010]  
MC9S12C32VPB25@TQFP52 [CX3010]      MC9S12C64CFA@TQFP48 [CX3007]  
MC9S12C64CFU@TQFP80 [CX3018]      MC9S12C64CPB@TQFP52 [CX3010]  
MC9S12C64MFA@TQFP48 [CX3007]      MC9S12C64MFU@TQFP80 [CX3018]  
MC9S12C64MPB@TQFP52 [CX3010]      MC9S12C64VFA@TQFP48 [CX3007]  
MC9S12C64VFU@TQFP80 [CX3018]      MC9S12C64VPB@TQFP52 [CX3010]  
MC9S12C96CFA@TQFP48 [CX3007]      MC9S12C96CFU@TQFP80 [CX3018]  
MC9S12C96CPB@TQFP52 [CX3010]      MC9S12C96MFA@TQFP48 [CX3007]  
MC9S12C96MFU@TQFP80 [CX3018]      MC9S12C96MPB@TQFP52 [CX3010]  
MC9S12C96VFA@TQFP48 [CX3007]      MC9S12C96VFU@TQFP80 [CX3018]  
MC9S12C96VPB@TQFP52 [CX3010]      MC9S12D32CFU@TQFP80 [CX3018]  
MC9S12D32MFU@TQFP80 [CX3018]      MC9S12D32VFU@TQFP80 [CX3018]  
MC9S12D64CFU@TQFP80 [CX3018]      MC9S12D64MFU@TQFP80 [CX3018]  
MC9S12D64VFU@TQFP80 [CX3018]      MC9S12DB128BCFU@TQFP80 [CX3018]  
MC9S12DB128BMFU@TQFP80 [CX3018]      MC9S12DB128BVFU@TQFP80 [CX3018]  
MC9S12DB128CFU@TQFP80 [CX3018]      MC9S12DB128MFU@TQFP80 [CX3018]  
MC9S12DB128VFU@TQFP80 [CX3018]      MC9S12DG128BCFU@TQFP80 [CX3018]  
MC9S12DG128BMFU@TQFP80 [CX3018]      MC9S12DG128BVFU@TQFP80 [CX3018]  
MC9S12DG128CFU@TQFP80 [CX3018]      MC9S12DG128ECFU@TQFP80 [CX3018]  
MC9S12DG128EMFU@TQFP80 [CX3018]      MC9S12DG128EVFU@TQFP80 [CX3018]  
MC9S12DG128MFU@TQFP80 [CX3018]      MC9S12DG128VFU@TQFP80 [CX3018]  
MC9S12DG256BCFU@TQFP80 [CX3018]      MC9S12DG256BMFU@TQFP80 [CX3018]  
MC9S12DG256BVFU@TQFP80 [CX3018]      MC9S12DG256CCFU@TQFP80 [CX3018]  
MC9S12DG256CFU@TQFP80 [CX3018]      MC9S12DG256CMFU@TQFP80 [CX3018]  
MC9S12DG256CVFU@TQFP80 [CX3018]      MC9S12DG256MFU@TQFP80 [CX3018]  
MC9S12DG256VFU@TQFP80 [CX3018]      MC9S12DJ128BCFU@TQFP80 [CX3018]  
MC9S12DJ128BMFU@TQFP80 [CX3018]      MC9S12DJ128BVFU@TQFP80 [CX3018]  
MC9S12DJ128CFU@TQFP80 [CX3018]      MC9S12DJ128ECFU@TQFP80 [CX3018]  
MC9S12DJ128EMFU@TQFP80 [CX3018]      MC9S12DJ128EVFU@TQFP80 [CX3018]  
MC9S12DJ128MFU@TQFP80 [CX3018]      MC9S12DJ128VFU@TQFP80 [CX3018]  
MC9S12DJ256BCFU@TQFP80 [CX3018]      MC9S12DJ256BMFU@TQFP80 [CX3018]  
MC9S12DJ256BVFU@TQFP80 [CX3018]      MC9S12DJ256CCFU@TQFP80 [CX3018]  
MC9S12DJ256CFU@TQFP80 [CX3018]      MC9S12DJ256CMFU@TQFP80 [CX3018]  
MC9S12DJ256CVFU@TQFP80 [CX3018]      MC9S12DJ256MFU@TQFP80 [CX3018]  
MC9S12DJ256VFU@TQFP80 [CX3018]      MC9S12DJ64CFU@TQFP80 [CX3018]  
MC9S12DJ64MFU@TQFP80 [CX3018]      MC9S12DJ64VFU@TQFP80 [CX3018]

MC9S12DP256BCFU@TQFP80 [CX3018]  
MC9S12DP256BVFU@TQFP80 [CX3018]  
MC9S12DP256CMFU@TQFP80 [CX3018]  
MC9S12DT128BCFU@TQFP80 [CX3018]  
MC9S12DT128BVFU@TQFP80 [CX3018]  
MC9S12DT128ECFU@TQFP80 [CX3018]  
MC9S12DT128EVFU@TQFP80 [CX3018]  
MC9S12DT128VFU@TQFP80 [CX3018]  
MC9S12DT256BMFU@TQFP80 [CX3018]  
MC9S12DT256CCFU@TQFP80 [CX3018]  
MC9S12DT256CMFU@TQFP80 [CX3018]  
MC9S12DT256MFU@TQFP80 [CX3018]  
MC9S12E128CFU@TQFP80 [CX3018]  
MC9S12E128MFU@TQFP80 [CX3018]  
MC9S12E128VFU@TQFP80 [CX3018]  
MC9S12E256CFU@TQFP80 [CX3018]  
MC9S12E256MFU@TQFP80 [CX3018]  
MC9S12E256VFU@TQFP80 [CX3018]  
MC9S12E32CFC@TQFP64 [CX4023]  
MC9S12E32CFU@TQFP80 [CX3018]  
MC9S12E32MFC@TQFP64 [CX4023]  
MC9S12E32MFU@TQFP80 [CX3018]  
MC9S12E32VFC@TQFP64 [CX4023]  
MC9S12E32VFU@TQFP80 [CX3018]  
MC9S12E64CFU@TQFP80 [CX3018]  
MC9S12E64MFU@TQFP80 [CX3018]  
MC9S12E64VFU@TQFP80 [CX3018]  
MC9S12GC128CFA@TQFP48 [CX3007]  
MC9S12GC128CPB@TQFP52 [CX3010]  
MC9S12GC128MFU@TQFP80 [CX3018]  
MC9S12GC128VFA@TQFP48 [CX3007]  
MC9S12GC128VPB@TQFP52 [CX3010]  
MC9S12GC16CFU@TQFP80 [CX3018]  
MC9S12GC16MFA@TQFP48 [CX3007]  
MC9S12GC16MPB@TQFP52 [CX3010]  
MC9S12GC16VFU@TQFP80 [CX3018]  
MC9S12GC32CFA@TQFP48 [CX3007]  
MC9S12GC32CPB@TQFP52 [CX3010]  
MC9S12GC32MFU@TQFP80 [CX3018]  
MC9S12GC32VFA@TQFP48 [CX3007]  
MC9S12GC32VPB@TQFP52 [CX3010]  
MC9S12GC64CFU@TQFP80 [CX3018]  
MC9S12GC64MFA@TQFP48 [CX3007]  
MC9S12GC64MPB@TQFP52 [CX3010]  
MC9S12GC64VFU@TQFP80 [CX3018]  
MC9S12GC96CFA@TQFP48 [CX3007]  
MC9S12GC96CPB@TQFP52 [CX3010]  
MC9S12GC96MFU@TQFP80 [CX3018]  
MC9S12GC96VFA@TQFP48 [CX3007]  
MC9S12GC96VPB@TQFP52 [CX3010]  
MC9S12Q128CFAE@TQFP48 [CX3007]  
MC9S12Q128CFUE@TQFP80 [CX3018]  
MC9S12Q128CPBE@TQFP52 [CX3010]  
MC9S12Q128MFAE@TQFP48 [CX3007]  
MC9S12Q128MFUE@TQFP80 [CX3018]  
MC9S12Q128MPBE@TQFP52 [CX3010]  
MC9S12Q128VFAE@TQFP48 [CX3007]  
MC9S12Q128VFUE@TQFP80 [CX3018]  
MC9S12Q128VPBE@TQFP52 [CX3010]

MC9S12DP256BMFU@TQFP80 [CX3018]  
MC9S12DP256CCFU@TQFP80 [CX3018]  
MC9S12DP256CVFU@TQFP80 [CX3018]  
MC9S12DT128BMFU@TQFP80 [CX3018]  
MC9S12DT128CFU@TQFP80 [CX3018]  
MC9S12DT128EMFU@TQFP80 [CX3018]  
MC9S12DT128MFU@TQFP80 [CX3018]  
MC9S12DT256BCFU@TQFP80 [CX3018]  
MC9S12DT256BVFU@TQFP80 [CX3018]  
MC9S12DT256CFU@TQFP80 [CX3018]  
MC9S12DT256CVFU@TQFP80 [CX3018]  
MC9S12DT256VFU@TQFP80 [CX3018]  
MC9S12E128CFUE@TQFP80 [CX3018]  
MC9S12E128MFUE@TQFP80 [CX3018]  
MC9S12E128VFUE@TQFP80 [CX3018]  
MC9S12E256CFUE@TQFP80 [CX3018]  
MC9S12E256MFUE@TQFP80 [CX3018]  
MC9S12E256VFUE@TQFP80 [CX3018]  
MC9S12E32CFCE@TQFP64 [CX4023]  
MC9S12E32CFUE@TQFP80 [CX3018]  
MC9S12E32MFCE@TQFP64 [CX4023]  
MC9S12E32MFUE@TQFP80 [CX3018]  
MC9S12E32VFCE@TQFP64 [CX4023]  
MC9S12E32VFUE@TQFP80 [CX3018]  
MC9S12E64CFUE@TQFP80 [CX3018]  
MC9S12E64MFUE@TQFP80 [CX3018]  
MC9S12E64VFUE@TQFP80 [CX3018]  
MC9S12GC128CFU@TQFP80 [CX3018]  
MC9S12GC128MFA@TQFP48 [CX3007]  
MC9S12GC128MPB@TQFP52 [CX3010]  
MC9S12GC128VFU@TQFP80 [CX3018]  
MC9S12GC16CFA@TQFP48 [CX3007]  
MC9S12GC16CPB@TQFP52 [CX3010]  
MC9S12GC16MFU@TQFP80 [CX3018]  
MC9S12GC16VFA@TQFP48 [CX3007]  
MC9S12GC16VPB@TQFP52 [CX3010]  
MC9S12GC32CFU@TQFP80 [CX3018]  
MC9S12GC32MFA@TQFP48 [CX3007]  
MC9S12GC32MPB@TQFP52 [CX3010]  
MC9S12GC32VFU@TQFP80 [CX3018]  
MC9S12GC64CFA@TQFP48 [CX3007]  
MC9S12GC64CPB@TQFP52 [CX3010]  
MC9S12GC64MFU@TQFP80 [CX3018]  
MC9S12GC64VFA@TQFP48 [CX3007]  
MC9S12GC64VPB@TQFP52 [CX3010]  
MC9S12GC96CFU@TQFP80 [CX3018]  
MC9S12GC96MFA@TQFP48 [CX3007]  
MC9S12GC96MPB@TQFP52 [CX3010]  
MC9S12GC96VFU@TQFP80 [CX3018]  
MC9S12Q128CFA@TQFP48 [CX3007]  
MC9S12Q128CFU@TQFP80 [CX3018]  
MC9S12Q128CPB@TQFP52 [CX3010]  
MC9S12Q128MFA@TQFP48 [CX3007]  
MC9S12Q128MFU@TQFP80 [CX3018]  
MC9S12Q128MPB@TQFP52 [CX3010]  
MC9S12Q128VFA@TQFP48 [CX3007]  
MC9S12Q128VFU@TQFP80 [CX3018]  
MC9S12Q128VPB@TQFP52 [CX3010]  
MC9S12Q32CFA@TQFP48 [CX3007]

MC9S12Q32CFAE@TQFP48 [CX3007]      MC9S12Q32CFU@TQFP80 [CX3018]  
MC9S12Q32CFUE@TQFP80 [CX3018]      MC9S12Q32CPB@TQFP52 [CX3010]  
MC9S12Q32CPBE@TQFP52 [CX3010]      MC9S12Q32MFA@TQFP48 [CX3007]  
MC9S12Q32MFAE@TQFP48 [CX3007]      MC9S12Q32MFU@TQFP80 [CX3018]  
MC9S12Q32MFUE@TQFP80 [CX3018]      MC9S12Q32MPB@TQFP52 [CX3010]  
MC9S12Q32MPBE@TQFP52 [CX3010]      MC9S12Q32VFA@TQFP48 [CX3007]  
MC9S12Q32VFAE@TQFP48 [CX3007]      MC9S12Q32VFU@TQFP80 [CX3018]  
MC9S12Q32VFUE@TQFP80 [CX3018]      MC9S12Q32VPB@TQFP52 [CX3010]  
MC9S12Q32VPBE@TQFP52 [CX3010]      MC9S12Q64CFA@TQFP48 [CX3007]  
MC9S12Q64CFAE@TQFP48 [CX3007]      MC9S12Q64CFU@TQFP80 [CX3018]  
MC9S12Q64CFUE@TQFP80 [CX3018]      MC9S12Q64CPB@TQFP52 [CX3010]  
MC9S12Q64CPBE@TQFP52 [CX3010]      MC9S12Q64MFA@TQFP48 [CX3007]  
MC9S12Q64MFAE@TQFP48 [CX3007]      MC9S12Q64MFU@TQFP80 [CX3018]  
MC9S12Q64MFUE@TQFP80 [CX3018]      MC9S12Q64MPB@TQFP52 [CX3010]  
MC9S12Q64MPBE@TQFP52 [CX3010]      MC9S12Q64VFA@TQFP48 [CX3007]  
MC9S12Q64VFAE@TQFP48 [CX3007]      MC9S12Q64VFU@TQFP80 [CX3018]  
MC9S12Q64VFUE@TQFP80 [CX3018]      MC9S12Q64VPB@TQFP52 [CX3010]  
MC9S12Q64VPBE@TQFP52 [CX3010]      MC9S12Q96CFA@TQFP48 [CX3007]  
MC9S12Q96CFAE@TQFP48 [CX3007]      MC9S12Q96CFU@TQFP80 [CX3018]  
MC9S12Q96CFUE@TQFP80 [CX3018]      MC9S12Q96CPB@TQFP52 [CX3010]  
MC9S12Q96CPBE@TQFP52 [CX3010]      MC9S12Q96MFA@TQFP48 [CX3007]  
MC9S12Q96MFAE@TQFP48 [CX3007]      MC9S12Q96MFU@TQFP80 [CX3018]  
MC9S12Q96MFUE@TQFP80 [CX3018]      MC9S12Q96MPB@TQFP52 [CX3010]  
MC9S12Q96MPBE@TQFP52 [CX3010]      MC9S12Q96VFA@TQFP48 [CX3007]  
MC9S12Q96VFAE@TQFP48 [CX3007]      MC9S12Q96VFU@TQFP80 [CX3018]  
MC9S12Q96VFUE@TQFP80 [CX3018]      MC9S12Q96VPB@TQFP52 [CX3010]  
MC9S12Q96VPBE@TQFP52 [CX3010]      MC9S12XS128CAA@QFP80 [CX3018]  
MC9S12XS128CAE@QFP64 [CX3011]      MC9S12XS128MAA@QFP80 [CX3018]  
MC9S12XS128MAE@QFP64 [CX3011]      MC9S12XS128VAA@QFP80 [CX3018]  
MC9S12XS128VAE@QFP64 [CX3011]      MC9S12XS256CAA@QFP80 [CX3018]  
MC9S12XS256CAE@QFP64 [CX3011]      MC9S12XS256MAA@QFP80 [CX3018]  
MC9S12XS256MAE@QFP64 [CX3011]      MC9S12XS256VAA@QFP80 [CX3018]  
MC9S12XS256VAE@QFP64 [CX3011]      MC9S12XS64CAA@QFP80 [CX3018]  
MC9S12XS64CAE@QFP64 [CX3011]      MC9S12XS64MAA@QFP80 [CX3018]  
MC9S12XS64MAE@QFP64 [CX3011]      MC9S12XS64VAA@QFP80 [CX3018]  
MC9S12XS64VAE@QFP64 [CX3011]      MCF51AC128ACFUE@QFP64 [CX3014]  
MCF51AC128ACLKE@LQFP80 [CX3017]      MCF51AC128ACPUE@LQFP64 [CX3011]  
MCF51AC128AMFUE@QFP64 [CX3014]      MCF51AC128AMLKE@LQFP80 [CX3017]  
MCF51AC128AMPUE@LQFP64 [CX3011]      MCF51AC128AVFUE@QFP64 [CX3014]  
MCF51AC128AVLKE@LQFP80 [CX3017]      MCF51AC128AVPUE@LQFP64 [CX3011]  
MCF51AC128BCFUE@QFP64 [CX3014]      MCF51AC128BCLKE@LQFP80 [CX3017]  
MCF51AC128BCPUE@LQFP64 [CX3011]      MCF51AC128BMFUE@QFP64 [CX3014]  
MCF51AC128BMLKE@LQFP80 [CX3017]      MCF51AC128BMPUE@LQFP64 [CX3011]  
MCF51AC128BVFUE@QFP64 [CX3014]      MCF51AC128BVLKE@LQFP80 [CX3017]  
MCF51AC128BVPUE@LQFP64 [CX3011]      MCF51AC128CCFUE@QFP64 [CX3014]  
MCF51AC128CCLKE@LQFP80 [CX3017]      MCF51AC128CCPUE@LQFP64 [CX3011]  
MCF51AC128CMFUE@QFP64 [CX3014]      MCF51AC128CMLKE@LQFP80 [CX3017]  
MCF51AC128CMPUE@LQFP64 [CX3011]      MCF51AC128CVFUE@QFP64 [CX3014]  
MCF51AC128CVLKE@LQFP80 [CX3017]      MCF51AC128CVPUE@LQFP64 [CX3011]  
MCF51AC128ACFUE@QFP64 [CX3014]      MCF51AC128ACLKE@LQFP80 [CX3017]  
MCF51AC128ACPUE@LQFP64 [CX3011]      MCF51AC128AMFUE@QFP64 [CX3014]  
MCF51AC128AMPUE@LQFP64 [CX3011]      MCF51AC128AVLKE@LQFP80 [CX3017]  
MCF51AC128AVFUE@QFP64 [CX3014]      MCF51AC128AVPUE@LQFP64 [CX3011]  
MCF51AC128BCFUE@QFP64 [CX3014]      MCF51AC128BCPUE@LQFP64 [CX3011]  
MCF51AC128BCLKE@LQFP80 [CX3017]      MCF51AC128BMLKE@LQFP80 [CX3017]  
MCF51AC128BMFUE@QFP64 [CX3014]      MCF51AC128BVFUE@QFP64 [CX3014]  
MCF51AC128BMPUE@LQFP64 [CX3011]      MCF51AC128BVPUE@LQFP64 [CX3011]  
MCF51AC128BVLKE@LQFP80 [CX3017]      MCF51AC128BVFUE@LQFP64 [CX3011]  
MCF51AC128CCFUE@QFP64 [CX3014]      MCF51AC128CCLKE@LQFP80 [CX3017]



MCF51AC256CCPUE@LQFP64 [CX3011] MCF51AC256CMFUE@QFP64 [CX3014]  
MCF51AC256CMLKE@LQFP80 [CX3017] MCF51AC256CMPUE@LQFP64 [CX3011]  
MCF51AC256CVFUE@QFP64 [CX3014] MCF51AC256CVLKE@LQFP80 [CX3017]  
MCF51AC256CVPUE@LQFP64 [CX3011] MCF51CN128CGT@QFN48 [CX4021]  
MCF51CN128CLH@LQFP64 [CX3011] MCF51CN128CLK@LQFP80 [CX3017]  
MCF51CN128MGT@QFN48 [CX4021] MCF51CN128MLH@LQFP64 [CX3011]  
MCF51CN128MLK@LQFP80 [CX3017] MCF51CN128VGT@QFN48 [CX4021]  
MCF51CN128VLH@LQFP64 [CX3011] MCF51CN128VLK@LQFP80 [CX3017]  
MCF51JE128CLK@QFP80 [CX3016] MCF51JE128CLL@QFP100 [CX3021]  
MCF51JE128MLK@QFP80 [CX3016] MCF51JE128MLL@QFP100 [CX3021]  
MCF51JE128VLK@QFP80 [CX3016] MCF51JE128VLL@QFP100 [CX3021]  
MCF51JE256CLK@QFP80 [CX3016] MCF51JE256CLL@QFP100 [CX3021]  
MCF51JE256MLK@QFP80 [CX3016] MCF51JE256MLL@QFP100 [CX3021]  
MCF51JE256VLK@QFP80 [CX3016] MCF51JE256VLL@QFP100 [CX3021]  
MCF51JM128CLD@LQFP44 [CX3005] MCF51JM128CLH@LQFP64 [CX3011]  
MCF51JM128CLK@LQFP80 [CX3017] MCF51JM128CQH@QFP64 [CX3014]  
MCF51JM128ECLK@LQFP80 [CX3017] MCF51JM128EMLK@LQFP80 [CX3017]  
MCF51JM128EVLK@LQFP80 [CX3017] MCF51JM128MLD@LQFP44 [CX3005]  
MCF51JM128MLH@LQFP64 [CX3011] MCF51JM128MLK@LQFP80 [CX3017]  
MCF51JM128MQH@QFP64 [CX3014] MCF51JM128VLD@LQFP44 [CX3005]  
MCF51JM128VLH@LQFP64 [CX3011] MCF51JM128VLK@LQFP80 [CX3017]  
MCF51JM128VQH@QFP64 [CX3014] MCF51JM32CLD@LQFP44 [CX3005]  
MCF51JM32CLH@LQFP64 [CX3011] MCF51JM32CLK@LQFP80 [CX3017]  
MCF51JM32CQH@QFP64 [CX3014] MCF51JM32ECLK@LQFP80 [CX3017]  
MCF51JM32EMLK@LQFP80 [CX3017] MCF51JM32EVLK@LQFP80 [CX3017]  
MCF51JM32MLD@LQFP44 [CX3005] MCF51JM32MLH@LQFP64 [CX3011]  
MCF51JM32MLK@LQFP80 [CX3017] MCF51JM32MQH@QFP64 [CX3014]  
MCF51JM32VLD@LQFP44 [CX3005] MCF51JM32VLH@LQFP64 [CX3011]  
MCF51JM32VLK@LQFP80 [CX3017] MCF51JM32VQH@QFP64 [CX3014]  
MCF51JM64CLD@LQFP44 [CX3005] MCF51JM64CLH@LQFP64 [CX3011]  
MCF51JM64CLK@LQFP80 [CX3017] MCF51JM64CQH@QFP64 [CX3014]  
MCF51JM64ECLK@LQFP80 [CX3017] MCF51JM64EMLK@LQFP80 [CX3017]  
MCF51JM64EVLK@LQFP80 [CX3017] MCF51JM64MLD@LQFP44 [CX3005]  
MCF51JM64MLH@LQFP64 [CX3011] MCF51JM64MLK@LQFP80 [CX3017]  
MCF51JM64MQH@QFP64 [CX3014] MCF51JM64VLD@LQFP44 [CX3005]  
MCF51JM64VLH@LQFP64 [CX3011] MCF51JM64VLK@LQFP80 [CX3017]  
MCF51JM64VQH@QFP64 [CX3014] MCF51QE128CLH@QFP64 [CX3011]  
MCF51QE128CLK@QFP80 [CX3017] MCF51QE128LH@QFP64 [CX3011]  
MCF51QE128LK@QFP80 [CX3017] MCF51QE128MLH@QFP64 [CX3011]  
MCF51QE128MLK@QFP80 [CX3017] MCF51QE128VLH@QFP64 [CX3011]  
MCF51QE128VLK@QFP80 [CX3017] MCF51QE32CLH@QFP64 [CX3011]  
MCF51QE32CLK@QFP80 [CX3017] MCF51QE32LH@QFP64 [CX3011]  
MCF51QE32LK@QFP80 [CX3017] MCF51QE32MLH@QFP64 [CX3011]  
MCF51QE32MLK@QFP80 [CX3017] MCF51QE32VLH@QFP64 [CX3011]  
MCF51QE32VLK@QFP80 [CX3017] MCF51QE64CLH@QFP64 [CX3011]  
MCF51QE64CLK@QFP80 [CX3017] MCF51QE64LH@QFP64 [CX3011]  
MCF51QE64LK@QFP80 [CX3017] MCF51QE64MLH@QFP64 [CX3011]  
MCF51QE64MLK@QFP80 [CX3017] MCF51QE64VLH@QFP64 [CX3011]  
MCF51QE64VLK@QFP80 [CX3017] MCF51QE96CLH@QFP64 [CX3011]  
MCF51QE96CLK@QFP80 [CX3017] MCF51QE96LH@QFP64 [CX3011]  
MCF51QE96LK@QFP80 [CX3017] MCF51QE96MLH@QFP64 [CX3011]  
MCF51QE96MLK@QFP80 [CX3017] MCF51QE96VLH@QFP64 [CX3011]  
MCF51QE96VLK@QFP80 [CX3017] MCHC908JW32FC@TQFN48 [CX4021]  
MCHC908JW32FCE@TQFN48 [CX4021] MM908E621ACDWB@SOIC54 [CX1060]  
MM908E622ACDWB@SOIC54 [CX1060] MM908E624ACDWB@SOIC54 [CX1060]  
MM908E624ACEW@SOIC54 [CX1060] MM908E624AYEW@SOIC54 [CX1060]  
MM908E625AVDWB@SOIC54 [CX1060] MM908E625AVEK@SOIC54 [CX1060]  
MM908E626AVDWB@SOIC54 [CX1060] MM908E626AVEK@SOIC54 [CX1060]  
PC56F8011VFAB@QFP32 [CX3001] PC56F8013VFAB@QFP32 [CX3001]

PC56F8014VFAE@QFP32 [CX3001]                   PC9S08SG4CSC@SOIC8 [CX1030]  
PC9S08SG4CSCE@SOIC8 [CX1030]                   PC9S08SG4CTG@TSSOP16 [CX1000]  
PC9S08SG4CTGE@TSSOP16 [CX1000]                PC9S08SG4CTJ@TSSOP20 [CX1000]  
PC9S08SG4CTJE@TSSOP20 [CX1000]               PC9S08SG4MSC@SOIC8 [CX1030]  
PC9S08SG4MSCE@SOIC8 [CX1030]                PC9S08SG4MTG@TSSOP16 [CX1000]  
PC9S08SG4MTGE@TSSOP16 [CX1000]               PC9S08SG4MTJ@TSSOP20 [CX1000]  
PC9S08SG4MTJE@TSSOP20 [CX1000]               PC9S08SG4VSC@SOIC8 [CX1030]  
PC9S08SG4VSCE@SOIC8 [CX1030]                PC9S08SG4VTG@TSSOP16 [CX1000]  
PC9S08SG4VTGE@TSSOP16 [CX1000]               PC9S08SG4VTJ@TSSOP20 [CX1000]  
PC9S08SG4VTJE@TSSOP20 [CX1000]               PC9S08SG8CSC@SOIC8 [CX1030]  
PC9S08SG8CSCE@SOIC8 [CX1030]                PC9S08SG8CTG@TSSOP16 [CX1000]  
PC9S08SG8CTGE@TSSOP16 [CX1000]               PC9S08SG8CTJ@TSSOP20 [CX1000]  
PC9S08SG8CTJE@TSSOP20 [CX1000]               PC9S08SG8MSC@SOIC8 [CX1030]  
PC9S08SG8MSCE@SOIC8 [CX1030]                PC9S08SG8MTG@TSSOP16 [CX1000]  
PC9S08SG8MTGE@TSSOP16 [CX1000]               PC9S08SG8MTJ@TSSOP20 [CX1000]  
PC9S08SG8MTJE@TSSOP20 [CX1000]               PC9S08SG8VSC@SOIC8 [CX1030]  
PC9S08SG8VSCE@SOIC8 [CX1030]                PC9S08SG8VTG@TSSOP16 [CX1000]  
PC9S08SG8VTGE@TSSOP16 [CX1000]               PC9S08SG8VTJ@TSSOP20 [CX1000]  
PC9S08SG8VTJE@TSSOP20 [CX1000]               PC9S08SH4CFK@QFN24 [CX4012]  
PC9S08SH4CFK@QFN24(auto trim) [CX4012]  
PC9S08SH4CFKE@QFN24 [CX4012]  
PC9S08SH4CFKE@QFN24(auto trim) [CX4012]  
PC9S08SH4CPJ                                    PC9S08SH4CPJ(auto trim)  
PC9S08SH4CPJE                                  PC9S08SH4CPJE(auto trim)  
PC9S08SH4CSC@SOIC8 [CX1030]  
PC9S08SH4CSC@SOIC8(auto trim) [CX1030]  
PC9S08SH4CSCE@SOIC8 [CX1030]  
PC9S08SH4CSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH4CTG@TSSOP16 [CX1000]  
PC9S08SH4CTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH4CTGE@TSSOP16 [CX1000]  
PC9S08SH4CTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH4CTJ@TSSOP20 [CX1000]  
PC9S08SH4CTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH4CTJE@TSSOP20 [CX1000]  
PC9S08SH4CTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH4CWJ@SOIC20 [CX1033]  
PC9S08SH4CWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH4CWJE@SOIC20 [CX1033]  
PC9S08SH4CWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH4MFK@QFN24 [CX4012]  
PC9S08SH4MFK@QFN24(auto trim) [CX4012]  
PC9S08SH4MFKE@QFN24 [CX4012]  
PC9S08SH4MFKE@QFN24(auto trim) [CX4012]  
PC9S08SH4MPJ                                   PC9S08SH4MPJ(auto trim)  
PC9S08SH4MPJE                                 PC9S08SH4MPJE(auto trim)  
PC9S08SH4MSC@SOIC8 [CX1030]  
PC9S08SH4MSC@SOIC8(auto trim) [CX1030]  
PC9S08SH4MSCE@SOIC8 [CX1030]  
PC9S08SH4MSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH4MTG@TSSOP16 [CX1000]  
PC9S08SH4MTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH4MTGE@TSSOP16 [CX1000]  
PC9S08SH4MTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH4MTJ@TSSOP20 [CX1000]  
PC9S08SH4MTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH4MTJE@TSSOP20 [CX1000]  
PC9S08SH4MTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH4MWJ@SOIC20 [CX1033]

PC9S08SH4MWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH4MWJE@SOIC20 [CX1033]  
PC9S08SH4MWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH4VFK@QFN24 [CX4012]  
PC9S08SH4VFK@QFN24(auto trim) [CX4012]  
PC9S08SH4VFK@QFN24 [CX4012]  
PC9S08SH4VFK@QFN24(auto trim) [CX4012]  
PC9S08SH4VPJ PC9S08SH4VPJ(auto trim)  
PC9S08SH4VPJE PC9S08SH4VPJE(auto trim)  
PC9S08SH4VSC@SOIC8 [CX1030]  
PC9S08SH4VSC@SOIC8(auto trim) [CX1030]  
PC9S08SH4VSCE@SOIC8 [CX1030]  
PC9S08SH4VSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH4VTG@TSSOP16 [CX1000]  
PC9S08SH4VTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH4VTG@TSSOP16 [CX1000]  
PC9S08SH4VTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH4VTJ@TSSOP20 [CX1000]  
PC9S08SH4VTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH4VTJE@TSSOP20 [CX1000]  
PC9S08SH4VTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH4VWJ@SOIC20 [CX1033]  
PC9S08SH4VWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH4VWJE@SOIC20 [CX1033]  
PC9S08SH4VWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH8CFK@QFN24 [CX4012]  
PC9S08SH8CFK@QFN24(auto trim) [CX4012]  
PC9S08SH8CFK@QFN24 [CX4012]  
PC9S08SH8CFK@QFN24(auto trim) [CX4012]  
PC9S08SH8CPJ PC9S08SH8CPJ(auto trim)  
PC9S08SH8CPJE PC9S08SH8CPJE(auto trim)  
PC9S08SH8CSC@SOIC8 [CX1030]  
PC9S08SH8CSC@SOIC8(auto trim) [CX1030]  
PC9S08SH8CSCE@SOIC8 [CX1030]  
PC9S08SH8CSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH8CTG@TSSOP16 [CX1000]  
PC9S08SH8CTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH8CTG@TSSOP16 [CX1000]  
PC9S08SH8CTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH8CTJ@TSSOP20 [CX1000]  
PC9S08SH8CTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH8CTJE@TSSOP20 [CX1000]  
PC9S08SH8CTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH8CWJ@SOIC20 [CX1033]  
PC9S08SH8CWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH8CWJE@SOIC20 [CX1033]  
PC9S08SH8CWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH8MFK@QFN24 [CX4012]  
PC9S08SH8MFK@QFN24(auto trim) [CX4012]  
PC9S08SH8MFK@QFN24 [CX4012]  
PC9S08SH8MFK@QFN24(auto trim) [CX4012]  
PC9S08SH8MPJ PC9S08SH8MPJ(auto trim)  
PC9S08SH8MPJE PC9S08SH8MPJE(auto trim)  
PC9S08SH8MSC@SOIC8 [CX1030]  
PC9S08SH8MSC@SOIC8(auto trim) [CX1030]  
PC9S08SH8MSCE@SOIC8 [CX1030]  
PC9S08SH8MSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH8MTG@TSSOP16 [CX1000]  
PC9S08SH8MTG@TSSOP16(auto trim) [CX1000]

PC9S08SH8MTGE@TSSOP16 [CX1000]  
PC9S08SH8MTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH8MTJ@TSSOP20 [CX1000]  
PC9S08SH8MTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH8MTJE@TSSOP20 [CX1000]  
PC9S08SH8MTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH8MWJ@SOIC20 [CX1033] PC9S08SH8MWJE@SOIC20 [CX1033]  
PC9S08SH8MWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH8VFK@QFN24 [CX4012]  
PC9S08SH8VFK@QFN24(auto trim) [CX4012]  
PC9S08SH8VFKE@QFN24 [CX4012]  
PC9S08SH8VFKE@QFN24(auto trim) [CX4012]  
PC9S08SH8VPJ PC9S08SH8VPJ(auto trim)  
PC9S08SH8VPJE PC9S08SH8VPJE(auto trim)  
PC9S08SH8VSC@SOIC8 [CX1030]  
PC9S08SH8VSC@SOIC8(auto trim) [CX1030]  
PC9S08SH8VSCE@SOIC8 [CX1030]  
PC9S08SH8VSCE@SOIC8(auto trim) [CX1030]  
PC9S08SH8VTG@TSSOP16 [CX1000]  
PC9S08SH8VTG@TSSOP16(auto trim) [CX1000]  
PC9S08SH8VTGE@TSSOP16 [CX1000]  
PC9S08SH8VTGE@TSSOP16(auto trim) [CX1000]  
PC9S08SH8VTJ@TSSOP20 [CX1000]  
PC9S08SH8VTJ@TSSOP20(auto trim) [CX1000]  
PC9S08SH8VTJE@TSSOP20 [CX1000]  
PC9S08SH8VTJE@TSSOP20(auto trim) [CX1000]  
PC9S08SH8VWJ@SOIC20 [CX1033]  
PC9S08SH8VWJ@SOIC20(auto trim) [CX1033]  
PC9S08SH8VWJE@SOIC20 [CX1033]  
PC9S08SH8VWJE@SOIC20(auto trim) [CX1033]  
PC9S08SH9MWJ@SOIC20(auto trim) [CX1033]  
S908QY2ACDT@TSSOP16 [CX1001]  
S908QY2ACDT@TSSOP16(a trim) [CX1001]  
S908QY2ACDTE@TSSOP16 [CX1001]  
S908QY2ACDTE@TSSOP16(a trim) [CX1001]  
S908QY2ACDW@SOIC16 [CX1033]  
S908QY2ACDW@SOIC16(a trim) [CX1033]  
S908QY2ACDWE@SOIC16 [CX1033]  
S908QY2ACDWE@SOIC16(a trim) [CX1033]  
S908QY2AMDT@TSSOP16 [CX1001]  
S908QY2AMDT@TSSOP16(a trim) [CX1001]  
S908QY2AMDTE@TSSOP16 [CX1001]  
S908QY2AMDTE@TSSOP16(a trim) [CX1001]  
S908QY2AMDW@SOIC16 [CX1033]  
S908QY2AMDW@SOIC16(a trim) [CX1033]  
S908QY2AMDWE@SOIC16 [CX1033]  
S908QY2AMDWE@SOIC16(a trim) [CX1033]  
S908QY2AVDT@TSSOP16 [CX1001]  
S908QY2AVDT@TSSOP16(a trim) [CX1001]  
S908QY2AVDTE@TSSOP16 [CX1001]  
S908QY2AVDTE@TSSOP16(a trim) [CX1001]  
S908QY2AVDW@SOIC16 [CX1033]  
S908QY2AVDW@SOIC16(a trim) [CX1033]  
S908QY2AVDWE@SOIC16 [CX1033]  
S908QY2AVDWE@SOIC16(a trim) [CX1033]  
S908QY4ACDT@TSSOP16 [CX1001]  
S908QY4ACDT@TSSOP16(a trim) [CX1001]  
S908QY4ACDTE@TSSOP16 [CX1001]  
S908QY4ACDTE@TSSOP16(a trim) [CX1001]

S908QY4ACDW@SOIC16 [CX1033]  
S908QY4ACDW@SOIC16(a trim) [CX1033]  
S908QY4ACDWE@SOIC16 [CX1033]  
S908QY4ACDWE@SOIC16(a trim) [CX1033]  
S908QY4AMDT@TSSOP16 [CX1001]  
S908QY4AMDT@TSSOP16(a trim) [CX1001]  
S908QY4AMDTE@TSSOP16 [CX1001]  
S908QY4AMDTE@TSSOP16(a trim) [CX1001]  
S908QY4AMDW@SOIC16 [CX1033]  
S908QY4AMDW@SOIC16(a trim) [CX1033]  
S908QY4AMDWE@SOIC16 [CX1033]  
S908QY4AMDWE@SOIC16(a trim) [CX1033]  
S908QY4AVDT@TSSOP16 [CX1001]  
S908QY4AVDT@TSSOP16(a trim) [CX1001]  
S908QY4AVDTE@TSSOP16 [CX1001]  
S908QY4AVDTE@TSSOP16(a trim) [CX1001]  
S908QY4AVDW@SOIC16 [CX1033]  
S908QY4AVDW@SOIC16(a trim) [CX1033]  
S908QY4AVDWE@SOIC16 [CX1033]  
S908QY4AVDWE@SOIC16(a trim) [CX1033]  
S9S08AW16ACFT [CX4021] S9S08AW16ACLM [CX3001]  
S9S08AW16ACLS [CX3003]  
S9S08AW16ACLS@QFP44(\*) [SA245A+B4404]  
S9S08AW16AMFT [CX4021] S9S08AW16AMLM [CX3001]  
S9S08AW16AMLS [CX3003]  
S9S08AW16AMLS@QFP44(\*) [SA245A+B4404]  
S9S08AW16AVFT [CX4021] S9S08AW16AVLM [CX3001]  
S9S08AW16AVLS [CX3003]  
S9S08AW16AVLS@QFP44(\*) [SA245A+B4404]  
S9S08AW8ACFT [CX4021] S9S08AW8ACLM [CX3001]  
S9S08AW8ACLS [CX3003]  
S9S08AW8ACLS@QFP44(\*) [SA245A+B4404]  
S9S08AW8AMFT [CX4021] S9S08AW8AMLM [CX3001]  
S9S08AW8AMLS [CX3003]  
S9S08AW8AMLS@QFP44(\*) [SA245A+B4404]  
S9S08AW8AVFT [CX4021] S9S08AW8AVLM [CX3001]  
S9S08AW8AVLS [CX3003]  
S9S08AW8AVLS@QFP44(\*) [SA245A+B4404]  
S9S08SG4CSC@SOIC8 [CX1030] S9S08SG4CSC@SOIC8 [CX1030]  
S9S08SG4CTG@TSSOP16 [CX1000] S9S08SG4CTGE@TSSOP16 [CX1000]  
S9S08SG4CTJ@TSSOP20 [CX1000] S9S08SG4CTJE@TSSOP20 [CX1000]  
S9S08SG4MSC@SOIC8 [CX1030] S9S08SG4MSCE@SOIC8 [CX1030]  
S9S08SG4MTG@TSSOP16 [CX1000] S9S08SG4MTGE@TSSOP16 [CX1000]  
S9S08SG4MTJ@TSSOP20 [CX1000] S9S08SG4MTJE@TSSOP20 [CX1000]  
S9S08SG4VSC@SOIC8 [CX1030] S9S08SG4VSCE@SOIC8 [CX1030]  
S9S08SG4VTG@TSSOP16 [CX1000] S9S08SG4VTGE@TSSOP16 [CX1000]  
S9S08SG4VTJ@TSSOP20 [CX1000] S9S08SG4VTJE@TSSOP20 [CX1000]  
S9S08SG8CSC@SOIC8 [CX1030] S9S08SG8CSCE@SOIC8 [CX1030]  
S9S08SG8CTG@TSSOP16 [CX1000] S9S08SG8CTGE@TSSOP16 [CX1000]  
S9S08SG8CTJ@TSSOP20 [CX1000] S9S08SG8CTJE@TSSOP20 [CX1000]  
S9S08SG8MSC@SOIC8 [CX1030] S9S08SG8MSCE@SOIC8 [CX1030]  
S9S08SG8MTG@TSSOP16 [CX1000] S9S08SG8MTGE@TSSOP16 [CX1000]  
S9S08SG8MTJ@TSSOP20 [CX1000] S9S08SG8MTJE@TSSOP20 [CX1000]  
S9S08SG8VSC@SOIC8 [CX1030] S9S08SG8VSCE@SOIC8 [CX1030]  
S9S08SG8VTG@TSSOP16 [CX1000] S9S08SG8VTGE@TSSOP16 [CX1000]  
S9S08SG8VTJ@TSSOP20 [CX1000] S9S08SG8VTJE@TSSOP20 [CX1000]  
S9S08SH4CFK@QFN24 [CX4012]  
S9S08SH4CFK@QFN24(auto trim) [CX4012]  
S9S08SH4CFKE@QFN24 [CX4012]

S9S08SH4CFKE@QFN24(auto trim) [CX4012]  
S9S08SH4CPJ S9S08SH4CPJ(auto trim)  
S9S08SH4CPJE S9S08SH4CPJE(auto trim)  
S9S08SH4CSC@SOIC8 [CX1030]  
S9S08SH4CSC@SOIC8(auto trim) [CX1030]  
S9S08SH4CSCE@SOIC8 [CX1030]  
S9S08SH4CSCE@SOIC8(auto trim) [CX1030]  
S9S08SH4CTG@TSSOP16 [CX1000]  
S9S08SH4CTG@TSSOP16(auto trim) [CX1000]  
S9S08SH4CTGE@TSSOP16 [CX1000]  
S9S08SH4CTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH4CTJ@TSSOP20 [CX1000]  
S9S08SH4CTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH4CTJE@TSSOP20 [CX1000]  
S9S08SH4CTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH4CWJ@SOIC20 [CX1033]  
S9S08SH4CWJ@SOIC20(auto trim) [CX1033]  
S9S08SH4CWJE@SOIC20 [CX1033]  
S9S08SH4CWJE@SOIC20(auto trim) [CX1033]  
S9S08SH4MFK@QFN24 [CX4012]  
S9S08SH4MFK@QFN24(auto trim) [CX4012]  
S9S08SH4MFKE@QFN24 [CX4012]  
S9S08SH4MFKE@QFN24(auto trim) [CX4012]  
S9S08SH4MPJ S9S08SH4MPJ(auto trim)  
S9S08SH4MPJE S9S08SH4MPJE(auto trim)  
S9S08SH4MSC@SOIC8 [CX1030]  
S9S08SH4MSC@SOIC8(auto trim) [CX1030]  
S9S08SH4MSCE@SOIC8 [CX1030]  
S9S08SH4MSCE@SOIC8(auto trim) [CX1030]  
S9S08SH4MTG@TSSOP16 [CX1000]  
S9S08SH4MTG@TSSOP16(auto trim) [CX1000]  
S9S08SH4MTGE@TSSOP16 [CX1000]  
S9S08SH4MTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH4MTJ@TSSOP20 [CX1000]  
S9S08SH4MTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH4MTJE@TSSOP20 [CX1000]  
S9S08SH4MTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH4MWJ@SOIC20 [CX1033]  
S9S08SH4MWJ@SOIC20(auto trim) [CX1033]  
S9S08SH4MWJE@SOIC20 [CX1033]  
S9S08SH4MWJE@SOIC20(auto trim) [CX1033]  
S9S08SH4VFK@QFN24 [CX4012]  
S9S08SH4VFK@QFN24(auto trim) [CX4012]  
S9S08SH4VFKE@QFN24 [CX4012]  
S9S08SH4VFKE@QFN24(auto trim) [CX4012]  
S9S08SH4VPJ S9S08SH4VPJ(auto trim)  
S9S08SH4VPJE S9S08SH4VPJE(auto trim)  
S9S08SH4VSC@SOIC8 [CX1030]  
S9S08SH4VSC@SOIC8(auto trim) [CX1030]  
S9S08SH4VSCE@SOIC8 [CX1030]  
S9S08SH4VSCE@SOIC8(auto trim) [CX1030]  
S9S08SH4VTG@TSSOP16 [CX1000]  
S9S08SH4VTG@TSSOP16(auto trim) [CX1000]  
S9S08SH4VTGE@TSSOP16 [CX1000]  
S9S08SH4VTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH4VTJ@TSSOP20 [CX1000]  
S9S08SH4VTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH4VTJE@TSSOP20 [CX1000]  
S9S08SH4VTJE@TSSOP20(auto trim) [CX1000]

S9S08SH4VWJ@SOIC20 [CX1033]  
S9S08SH4VWJ@SOIC20(auto trim) [CX1033]  
S9S08SH4VWJE@SOIC20 [CX1033]  
S9S08SH4VWJE@SOIC20(auto trim) [CX1033]  
S9S08SH8CFK@QFN24 [CX4012]  
S9S08SH8CFK@QFN24(auto trim) [CX4012]  
S9S08SH8CFKE@QFN24 [CX4012]  
S9S08SH8CFKE@QFN24(auto trim) [CX4012]  
S9S08SH8CPJ S9S08SH8CPJ(auto trim)  
S9S08SH8CPJE S9S08SH8CPJE(auto trim)  
S9S08SH8CSC@SOIC8 [CX1030]  
S9S08SH8CSC@SOIC8(auto trim) [CX1030]  
S9S08SH8CSCE@SOIC8 [CX1030]  
S9S08SH8CSCE@SOIC8(auto trim) [CX1030]  
S9S08SH8CTG@TSSOP16 [CX1000]  
S9S08SH8CTG@TSSOP16(auto trim) [CX1000]  
S9S08SH8CTGE@TSSOP16 [CX1000]  
S9S08SH8CTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH8CTJ@TSSOP20 [CX1000]  
S9S08SH8CTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH8CTJE@TSSOP20 [CX1000]  
S9S08SH8CTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH8CWJ@SOIC20 [CX1033]  
S9S08SH8CWJ@SOIC20(auto trim) [CX1033]  
S9S08SH8CWJE@SOIC20 [CX1033]  
S9S08SH8CWJE@SOIC20(auto trim) [CX1033]  
S9S08SH8MFK@QFN24 [CX4012]  
S9S08SH8MFK@QFN24(auto trim) [CX4012]  
S9S08SH8MFKE@QFN24 [CX4012]  
S9S08SH8MFKE@QFN24(auto trim) [CX4012]  
S9S08SH8MPJ S9S08SH8MPJ(auto trim)  
S9S08SH8MPJE S9S08SH8MPJE(auto trim)  
S9S08SH8MSC@SOIC8 [CX1030]  
S9S08SH8MSC@SOIC8(auto trim) [CX1030]  
S9S08SH8MSCE@SOIC8 [CX1030]  
S9S08SH8MSCE@SOIC8(auto trim) [CX1030]  
S9S08SH8MTG@TSSOP16 [CX1000]  
S9S08SH8MTG@TSSOP16(auto trim) [CX1000]  
S9S08SH8MTGE@TSSOP16 [CX1000]  
S9S08SH8MTGE@TSSOP16(auto trim) [CX1000]  
S9S08SH8MTJ@TSSOP20 [CX1000]  
S9S08SH8MTJ@TSSOP20(auto trim) [CX1000]  
S9S08SH8MTJE@TSSOP20 [CX1000]  
S9S08SH8MTJE@TSSOP20(auto trim) [CX1000]  
S9S08SH8MWJ@SOIC20 [CX1033] S9S08SH8MWJE@SOIC20 [CX1033]  
S9S08SH8MWJE@SOIC20(auto trim) [CX1033]  
S9S08SH8VFK@QFN24 [CX4012]  
S9S08SH8VFK@QFN24(auto trim) [CX4012]  
S9S08SH8VFKE@QFN24 [CX4012]  
S9S08SH8VFKE@QFN24(auto trim) [CX4012]  
S9S08SH8VPJ S9S08SH8VPJ(auto trim)  
S9S08SH8VPJE S9S08SH8VPJE(auto trim)  
S9S08SH8VSC@SOIC8 [CX1030]  
S9S08SH8VSC@SOIC8(auto trim) [CX1030]  
S9S08SH8VSCE@SOIC8 [CX1030]  
S9S08SH8VSCE@SOIC8(auto trim) [CX1030]  
S9S08SH8VTG@TSSOP16 [CX1000]  
S9S08SH8VTG@TSSOP16(auto trim) [CX1000]  
S9S08SH8VTGE@TSSOP16 [CX1000]





LPC2367FET100 [CX5055]  
LPC2368FET100 [CX5055]  
LPC2387FET100 [CX5055]  
P89C668@PLCC44 [CX2044]

LPC2368@QFP100 [CX3021-4]  
LPC2368FET100N [CX5055]  
P89C668 [CX0001]  
P89C668@TQFP44 [CX3002]

## MXIC

### E (E) PROM/FRAM/NVRAM

MX30LF1208AA@FBGA63 [CX5046]  
MX30LF1G08AA@TSOP48 [CX1004-3]

MX30LF1208AA@TSOP48 [CX1004-3]

## MY-MS

### E (E) PROM/FRAM/NVRAM

MM24C01-2/3@SOIC8 [CX1045]  
MM24C01-3@SOIC8 [CX1045]  
MM24C02-3 [CX0001]  
MM24C04-2/3@SOIC8 [CX1045]  
MM24C04-3@SOIC8 [CX1045]  
MM24C08-3 [CX0001]  
MM24C16-2/3@SOIC8 [CX1045]  
MM24C16-3@SOIC8 [CX1045]

MM24C01-3 [CX0001]  
MM24C02-2/3@SOIC8 [CX1045]  
MM24C02-3@SOIC8 [CX1045]  
MM24C04-3 [CX0001]  
MM24C08-2/3@SOIC8 [CX1045]  
MM24C08-3@SOIC8 [CX1045]  
MM24C16-3 [CX0001]

## MYSON

### MICROCONTROLLER

CS8954F@PQFP44 [CX3002]  
CS8954V@PLCC44 [CX2044]  
CS8955G@LQFP48 [CX3007]  
CS8955HG@LQFP48 [CX3007]  
CS8955HV@PLCC44 [CX2044]  
CS8955V@PLCC44 [CX2044]  
MTV212MN64I [CX0001]  
MTV212MS64I@SDIP42 [CX0042]  
MTV212MV64I@PLCC44 [CX2044]  
MTV230GMS@SDIP42 [CX0042]  
MTV230MF@TQFP44 [CX3002]  
MTV230MV@PLCC44 [CX2044]  
MTV230PMS@SDIP42 [CX0042]  
MTV312MN64(AG VERSION) [CX0001]  
MTV312MS64(AG VERSION)@SDIP42 [CX0042]  
MTV312MS64(AJ VERSION)@SDIP42 [CX0042]  
MTV312MV64(AG VERSION)@PLCC44 [CX2044]  
MTV312MV64(AJ VERSION)@PLCC44 [CX2044]  
MTV412MF128@PQFP44 [CX3002]  
MTV412MV128@PLCC44 [CX2044]  
MTV416GMG@TQFP48 [CX3007]  
MTV416MF@TQFP44 [CX3002]  
MTV416MV@PLCC44 [CX2044]  
MTV416PMG@TQFP48 [CX3007]  
MTV512MF(A1 VERSION)@TQFP44 [CX3002]  
MTV512MF(A3 VERSION)@TQFP44 [CX3002]  
MTV512MV(A1 VERSION)@PLCC44 [CX2044]

CS8954N [CX0001]  
CS8955F@PQFP44 [CX3002]  
CS8955HF@PQFP44 [CX3002]  
CS8955HN [CX0001]  
CS8955N [CX0001]  
MTV212MN32 [CX0001]  
MTV212MS32@SDIP42 [CX0042]  
MTV212MV32@PLCC44 [CX2044]  
MTV230GMF@TQFP44 [CX3002]  
MTV230GMV@PLCC44 [CX2044]  
MTV230MS@SDIP42 [CX0042]  
MTV230PMF@TQFP44 [CX3002]  
MTV230PMV@PLCC44 [CX2044]  
MTV312MN64(AJ VERSION) [CX0001]  
MTV412MS128@SDIP42 [CX0042]  
MTV416GMF@TQFP44 [CX3002]  
MTV416GMV@PLCC44 [CX2044]  
MTV416MG@TQFP48 [CX3007]  
MTV416PMF@TQFP44 [CX3002]  
MTV416PMV@PLCC44 [CX2044]

## NANSI

### E (E) PROM/FRAM/NVRAM

N25S10 [CX0001]	N25S10@SOP8 [CX1045#1]
N25S10@VDFN8 [CX4005#1]	N25S16 [CX0001#1]
N25S16@SOIC16 [CX1033#1]	N25S16@SOIC8 [CX1044#1]
N25S16@WSON8 [CX4005#1]	N25S20 [CX0001]
N25S20@SOP8 [CX1045#1]	N25S20@VDFN8 [CX4005#1]
N25S32 [CX0001#1]	N25S32@SOIC16 [CX1033#1]
N25S32@SOIC8 [CX1044#1]	N25S32@WSON8 [CX4005#1]
N25S40 [CX0001]	N25S40@SOIC8[150mil] [CX1045#1]
N25S40@SOIC8[200mil] [CX1044#1]	N25S40@WSON8 [CX4005#1]
N25S80 [CX0001#1]	N25S80@SOP16 [CX1033#1]
N25S80@SOP8 [CX1044#1]	N25S80@VDFN8 [CX4005#1]

## NANTRONICS

### E (E) PROM/FRAM/NVRAM

N25S32 [CX0001#1]	N25S32@SOIC16 [CX1033#1]
N25S32@SOIC8 [CX1044#1]	N25S32@WSON8 [CX4005#1]
N25S80 [CX0001]	N25S80@SOIC8[150mil] [CX1045#1]
N25S80@SOIC8[200mil] [CX1044#1]	N25S80@WSON8 [CX4005#1]

## NATRONICS

### E (E) PROM/FRAM/NVRAM

NS29LV032FB@FBGA48 [CX5002]	NS29LV032FB@TSOP48 [CX1004]
NS29LV032FT@FBGA48 [CX5002]	NS29LV032FT@TSOP48 [CX1004]

## NEC

### E (E) PROM/FRAM/NVRAM

D2716D [CX0001]	uPD271000 [CX0001]
uPD271000@PLCC32 [CX2032]	uPD271000@TSOP32 [CX1002]
uPD27128 [CX0001]	uPD27128(C) [CX0001]
uPD27128(D) [CX0001]	uPD2716 [CX0001]
uPD27256 [CX0001]	uPD27256(C) [CX0001]
uPD27256(D) [CX0001]	uPD27256A [CX0001]
uPD27256A(C) [CX0001]	uPD27256A(D) [CX0001]
uPD2732 [CX0001]	uPD2732A [CX0001]
uPD27512 [CX0001]	uPD27512ACT [CX0001]
uPD27512AD [CX0001]	uPD2764 [CX0001]
uPD2764C [CX0001]	uPD2764D [CX0001]
uPD27C1000 [CX0001]	uPD27C1000@PLCC32 [CX2032]
uPD27C1000@TSOP32 [CX1002]	uPD27C1000A [CX0001]
uPD27C1000A@PLCC32 [CX2032]	uPD27C1000A@TSOP32 [CX1002]
uPD27C1000AD [CX0001]	uPD27C1000AD@PLCC32 [CX2032]
uPD27C1000AD@TSOP32 [CX1002]	uPD27C1001 [CX0001]
uPD27C1001@PLCC32 [CX2032]	uPD27C1001@TSOP32 [CX1002]

uPD27C1001A [CX0001]  
uPD27C1001A@TSOP32 [CX1002]  
uPD27C1001D@PLCC32 [CX2032]  
uPD27C1024 [CX0001]  
uPD27C2001 [CX0001]  
uPD27C2001@TSOP32 [CX1002]  
uPD27C2001D@PLCC32 [CX2032]  
uPD27C210 [CX0001]  
uPD27C256A [CX0001]  
uPD27C4001 [CX0001]  
uPD27C4001@TSOP32 [CX1002]  
uPD27C512 [CX0001]  
uPD27C64(D) [CX0001]  
uPD27C8001 [CX0001]  
uPD27C8001@TSOP32 [CX1002]  
uPD28C04@SOIC24 [CX1033]  
uPD28C05@SOIC24 [CX1033]  
uPD28C64 [CX0001]  
uPD29F008CB@TSOP40 [CX1006]

uPD27C1001A@PLCC32 [CX2032]  
uPD27C1001D [CX0001]  
uPD27C1001D@TSOP32 [CX1002]  
uPD27C1024A [CX0001]  
uPD27C2001@PLCC32 [CX2032]  
uPD27C2001D [CX0001]  
uPD27C2001D@TSOP32 [CX1002]  
uPD27C256 [CX0001]  
uPD27C400 [CX0001]  
uPD27C4001@PLCC32 [CX2032]  
uPD27C4096 [CX0001]  
uPD27C64(C) [CX0001]  
uPD27C8000 [CX0001]  
uPD27C8001@PLCC32 [CX2032]  
uPD28C04 [CX0001]  
uPD28C05 [CX0001]  
uPD28C256 [CX0001]  
uPD28C64@SOIC28 [CX1033]  
uPD29F008CT@TSOP40 [CX1006]

#### MICROCONTROLLER

R5F1006AASP [CX1026]  
R5F1006CASP [CX1026]  
R5F1006DASP [CX1026]  
R5F1006EASP [CX1026]  
R5F1006FASP [CX1026]  
R5F1006GASP [CX1026]  
R5F1006HASP [CX1026]  
R5F1006JASP [CX1026]  
R5F1006KASP [CX1026]  
R5F1006LASP [CX1026]  
R5F1007AANA [CX4012]  
R5F1007CANA [CX4012]  
R5F1007DANA [CX4012]  
R5F1007EANA [CX4012]  
R5F1007FANA [CX4012]  
R5F1007GANA [CX4012]  
R5F1007HANA [CX4012]  
R5F1007JANA [CX4012]  
R5F1007KANA [CX4012]  
R5F1007LANA [CX4012]  
R5F1008AALA [CX0001]  
R5F1008CALA [CX0001]  
R5F1008DALA [CX0001]  
R5F1008EALA [CX0001]  
R5F1008FALA [CX0001]  
R5F1008GALA [CX0001]  
R5F1008HALA [CX0001]  
R5F1008JALA [CX0001]  
R5F1008KALA [CX0001]  
R5F1008LALA [CX0001]  
R5F100AAASP [CX1026]  
R5F100ACASP [CX1026]  
R5F100ADASP [CX1026]  
R5F100AEASP [CX1026]  
R5F100AFASP [CX1026]  
R5F100AGASP [CX1026]  
R5F100AHASP [CX1026]

R5F1006ADSP [CX1026]  
R5F1006CDSP [CX1026]  
R5F1006DDSP [CX1026]  
R5F1006EDSP [CX1026]  
R5F1006FDSP [CX1026]  
R5F1006GDSP [CX1026]  
R5F1006HDSP [CX1026]  
R5F1006JDSP [CX1026]  
R5F1006KDSP [CX1026]  
R5F1006LDSP [CX1026]  
R5F1007ADNA [CX4012]  
R5F1007CDNA [CX4012]  
R5F1007DDNA [CX4012]  
R5F1007EDNA [CX4012]  
R5F1007FDNA [CX4012]  
R5F1007GDNA [CX4012]  
R5F1007HDNA [CX4012]  
R5F1007JDNA [CX4012]  
R5F1007KDNA [CX4012]  
R5F1007LDNA [CX4012]  
R5F1008ADLA [CX0001]  
R5F1008CDLA [CX0001]  
R5F1008DDLA [CX0001]  
R5F1008EDLA [CX0001]  
R5F1008FDLA [CX0001]  
R5F1008GDLA [CX0001]  
R5F1008HDLA [CX0001]  
R5F1008JDLA [CX0001]  
R5F1008KDLA [CX0001]  
R5F1008LDLA [CX0001]  
R5F100AADSP [CX1026]  
R5F100ACDSP [CX1026]  
R5F100ADDSP [CX1026]  
R5F100AEDSP [CX1026]  
R5F100AFDSP [CX1026]  
R5F100AGDSP [CX1026]  
R5F100AHDSP [CX1026]

R5F100AJASP [CX1026]	R5F100AJDSP [CX1026]
R5F100AKASP [CX1026]	R5F100AKDSP [CX1026]
R5F100ALASP [CX1026]	R5F100ALDSP [CX1026]
R5F100BAANA [CX4015]	R5F100BADNA [CX4015]
R5F100BCANA [CX4015]	R5F100BCDNA [CX4015]
R5F100BDANA [CX4015]	R5F100BDDNA [CX4015]
R5F100BEANA [CX4015]	R5F100BEDNA [CX4015]
R5F100BFANA [CX4015]	R5F100BFDNA [CX4015]
R5F100BGANA [CX4015]	R5F100BGDNA [CX4015]
R5F100BHANA [CX4015]	R5F100BHDNA [CX4015]
R5F100BJANA [CX4015]	R5F100BJDNA [CX4015]
R5F100BKANA [CX4015]	R5F100BKDNA [CX4015]
R5F100BLANA [CX4015]	R5F100BLDNA [CX4015]
R5F100CAALA [CX0001]	R5F100CADLA [CX0001]
R5F100CCALA [CX0001]	R5F100CCDLA [CX0001]
R5F100CDALA [CX0001]	R5F100CDDLA [CX0001]
R5F100CEALA [CX0001]	R5F100CEDLA [CX0001]
R5F100CFALA [CX0001]	R5F100CFDLA [CX0001]
R5F100CGALA [CX0001]	R5F100CGDLA [CX0001]
R5F100CHALA [CX0001]	R5F100CHDLA [CX0001]
R5F100CJALA [CX0001]	R5F100CJDLA [CX0001]
R5F100CKALA [CX0001]	R5F100CKDLA [CX0001]
R5F100CLALA [CX0001]	R5F100CLDLA [CX0001]
R5F100EAANA [CX4017]	R5F100EADNA [CX4017]
R5F100ECANA [CX4017]	R5F100ECDNA [CX4017]
R5F100EDANA [CX4017]	R5F100EDDNA [CX4017]
R5F100EEANA [CX4017]	R5F100EEDNA [CX4017]
R5F100EFANA [CX4017]	R5F100EFDNA [CX4017]
R5F100EGANA [CX4017]	R5F100EGDNA [CX4017]
R5F100EHANA [CX4017]	R5F100EHDNA [CX4017]
R5F100EJANA [CX4017]	R5F100EJDNA [CX4017]
R5F100EKANA [CX4017]	R5F100EKDNA [CX4017]
R5F100ELANA [CX4017]	R5F100ELDNA [CX4017]
R5F100FAAFP [CX3005]	R5F100FADFP [CX3005]
R5F100FCAFP [CX3005]	R5F100FCDFP [CX3005]
R5F100FDAFP [CX3005]	R5F100FDDFP [CX3005]
R5F100FEAFP [CX3005]	R5F100FEDFP [CX3005]
R5F100FFAFP [CX3005]	R5F100FFDFP [CX3005]
R5F100FGAFP [CX3005]	R5F100FGDFP [CX3005]
R5F100FHAFP [CX3005]	R5F100FHDFP [CX3005]
R5F100FJAFP [CX3005]	R5F100FJDFP [CX3005]
R5F100FKAFP [CX3005]	R5F100FKDFP [CX3005]
R5F100FLAFP [CX3005]	R5F100FLDFP [CX3005]
R5F100GAAFB [CX3007]	R5F100GAANA [CX4021]
R5F100GADFB [CX3007]	R5F100GADNA [CX4021]
R5F100GCAFB [CX3007]	R5F100GCANA [CX4021]
R5F100GCDFB [CX3007]	R5F100GCDNA [CX4021]
R5F100GDAFB [CX3007]	R5F100GDANA [CX4021]
R5F100GDDFB [CX3007]	R5F100GDDNA [CX4021]
R5F100GEAFB [CX3007]	R5F100GEANA [CX4021]
R5F100GEDFB [CX3007]	R5F100GEDNA [CX4021]
R5F100GFAFB [CX3007]	R5F100GFANA [CX4021]
R5F100GFDFB [CX3007]	R5F100GFDNA [CX4021]
R5F100GGAFB [CX3007]	R5F100GGANA [CX4021]
R5F100GGDFB [CX3007]	R5F100GGDNA [CX4021]
R5F100GHAFB [CX3007]	R5F100GHANA [CX4021]
R5F100GHDFB [CX3007]	R5F100GHDNA [CX4021]
R5F100GJAFB [CX3007]	R5F100GJANA [CX4021]
R5F100GJDFB [CX3007]	R5F100GJDNA [CX4021]

R5F100GKAFB [CX3007]	R5F100GKANA [CX4021]
R5F100GKDFB [CX3007]	R5F100GKDNA [CX4021]
R5F100GLAFB [CX3007]	R5F100GLANA [CX4021]
R5F100GLDFB [CX3007]	R5F100GLDNA [CX4021]
R5F100JCAFA [CX3010]	R5F100JCDFB [CX3010]
R5F100JDAFA [CX3010]	R5F100JDDFA [CX3010]
R5F100JEAFB [CX3010]	R5F100JEDFA [CX3010]
R5F100JFAFA [CX3010]	R5F100JFDFA [CX3010]
R5F100JGAFA [CX3010]	R5F100JGDFA [CX3010]
R5F100JHAFA [CX3010]	R5F100JHDFB [CX3010]
R5F100JJAFA [CX3010]	R5F100JJDFB [CX3010]
R5F100JKAFB [CX3010]	R5F100JKDFB [CX3010]
R5F100JLAFA [CX3010]	R5F100JLDFB [CX3010]
R5F100LCABG [CX0001]	R5F100LCAFA [CX3012]
R5F100LCAFB [CX3011]	R5F100LCAFC [CX3085]
R5F100LCDBG [CX0001]	R5F100LCDFA [CX3012]
R5F100LCDFB [CX3011]	R5F100LCDFC [CX3085]
R5F100LDABG [CX0001]	R5F100LDAFA [CX3012]
R5F100LDAFB [CX3011]	R5F100LDAFC [CX3085]
R5F100LDDBG [CX0001]	R5F100LDDFA [CX3012]
R5F100LDDFB [CX3011]	R5F100LDDFC [CX3085]
R5F100LEABG [CX0001]	R5F100LEAFB [CX3012]
R5F100LEAFB [CX3011]	R5F100LEAFC [CX3085]
R5F100LEDBG [CX0001]	R5F100LEDFA [CX3012]
R5F100LEDFB [CX3011]	R5F100LEDFC [CX3085]
R5F100LFABG [CX0001]	R5F100LFAFA [CX3012]
R5F100LFAFB [CX3011]	R5F100LFAFC [CX3085]
R5F100LFDBG [CX0001]	R5F100LFDFA [CX3012]
R5F100LFDFB [CX3011]	R5F100LFDFC [CX3085]
R5F100LGABG [CX0001]	R5F100LGAFB [CX3012]
R5F100LGAFB [CX3011]	R5F100LGAFC [CX3085]
R5F100LGDBG [CX0001]	R5F100LGDFA [CX3012]
R5F100LGDFB [CX3011]	R5F100LGDFC [CX3085]
R5F100LHABG [CX0001]	R5F100LHAFA [CX3012]
R5F100LHAFB [CX3011]	R5F100LHAFC [CX3085]
R5F100LHDBG [CX0001]	R5F100LHDFB [CX3012]
R5F100LHDFB [CX3011]	R5F100LHDFC [CX3085]
R5F100LJABG [CX0001]	R5F100LJAFA [CX3012]
R5F100LJAFB [CX3011]	R5F100LJAFC [CX3085]
R5F100LJDBG [CX0001]	R5F100LJDFA [CX3012]
R5F100LJDFB [CX3011]	R5F100LJDFC [CX3085]
R5F100LKABG [CX0001]	R5F100LKAFB [CX3012]
R5F100LKAFB [CX3011]	R5F100LKAFC [CX3085]
R5F100LKDBG [CX0001]	R5F100LKDFB [CX3012]
R5F100LKDFB [CX3011]	R5F100LKDFC [CX3085]
R5F100LLABG [CX0001]	R5F100LLAFA [CX3012]
R5F100LLAFB [CX3011]	R5F100LLAFC [CX3085]
R5F100LLDBG [CX0001]	R5F100LLDFA [CX3012]
R5F100LLDFB [CX3011]	R5F100LLDFC [CX3085]
R5F100MCAFA [CX3017]	R5F100MCAFB [CX3016]
R5F100MCDFA [CX3017]	R5F100MCDFB [CX3016]
R5F100MDAFA [CX3017]	R5F100MDAFB [CX3016]
R5F100MDDFA [CX3017]	R5F100MDDFB [CX3016]
R5F100MEAFA [CX3017]	R5F100MEAFB [CX3016]
R5F100MEDFA [CX3017]	R5F100MEDFB [CX3016]
R5F100MFAFA [CX3017]	R5F100MFAFB [CX3016]
R5F100MFDFA [CX3017]	R5F100MFDFB [CX3016]
R5F100MGAFB [CX3017]	R5F100MGAFB [CX3016]
R5F100MGDFA [CX3017]	R5F100MGDFB [CX3016]

R5F100MHAF A [CX3017]	R5F100MHAF B [CX3016]
R5F100MHDF A [CX3017]	R5F100MHDF B [CX3016]
R5F100MJAF A [CX3017]	R5F100MJAF B [CX3016]
R5F100MJDF A [CX3017]	R5F100MJDF B [CX3016]
R5F100MKAF A [CX3017]	R5F100MKAF B [CX3016]
R5F100MKDF A [CX3017]	R5F100MKDF B [CX3016]
R5F100MLAF A [CX3017]	R5F100MLAF B [CX3016]
R5F100MLDF A [CX3017]	R5F100MLDF B [CX3016]
R5F100PCAF A [CX3062]	R5F100PCAF B [CX3021]
R5F100PCDF A [CX3062]	R5F100PCDF B [CX3021]
R5F100PDAF A [CX3062]	R5F100PDAF B [CX3021]
R5F100PDDF A [CX3062]	R5F100PDDF B [CX3021]
R5F100PEAF A [CX3062]	R5F100PEAF B [CX3021]
R5F100PEDF A [CX3062]	R5F100PEDF B [CX3021]
R5F100PF AF A [CX3062]	R5F100PF AF B [CX3021]
R5F100PFDF A [CX3062]	R5F100PFDF B [CX3021]
R5F100PGAF A [CX3062]	R5F100PGAF B [CX3021]
R5F100PGDF A [CX3062]	R5F100PGDF B [CX3021]
R5F100PHAF A [CX3062]	R5F100PHAF B [CX3021]
R5F100PHDF A [CX3062]	R5F100PHDF B [CX3021]
R5F100PJAF A [CX3062]	R5F100PJAF B [CX3021]
R5F100PJDF A [CX3062]	R5F100PJDF B [CX3021]
R5F100PKAF A [CX3062]	R5F100PKAF B [CX3021]
R5F100PKDF A [CX3062]	R5F100PKDF B [CX3021]
R5F100PLAF A [CX3062]	R5F100PLAF B [CX3021]
R5F100PLDF A [CX3062]	R5F100PLDF B [CX3021]
R5F100SCAF B [CX3031]	R5F100SCDF B [CX3031]
R5F100SDAF B [CX3031]	R5F100SDDF B [CX3031]
R5F100SEAF B [CX3031]	R5F100SEDF B [CX3031]
R5F100SF AF B [CX3031]	R5F100SFDF B [CX3031]
R5F100SGAF B [CX3031]	R5F100SGDF B [CX3031]
R5F100SHAF B [CX3031]	R5F100SHDF B [CX3031]
R5F100SJAF B [CX3031]	R5F100SJDF B [CX3031]
R5F100SKAF B [CX3031]	R5F100SKDF B [CX3031]
R5F100SLAF B [CX3031]	R5F100SLDF B [CX3031]
R5F1016AASP [CX1026]	R5F1016ADSP [CX1026]
R5F1016CASP [CX1026]	R5F1016CDSP [CX1026]
R5F1016DASP [CX1026]	R5F1016DDSP [CX1026]
R5F1016EASP [CX1026]	R5F1016EDSP [CX1026]
R5F1016FASP [CX1026]	R5F1016FDSP [CX1026]
R5F1016GASP [CX1026]	R5F1016GDSP [CX1026]
R5F1016HASP [CX1026]	R5F1016HDSP [CX1026]
R5F1016JASP [CX1026]	R5F1016JDSP [CX1026]
R5F1016KASP [CX1026]	R5F1016KDSP [CX1026]
R5F1016LASP [CX1026]	R5F1016LDSP [CX1026]
R5F1017AANA [CX4012]	R5F1017ADNA [CX4012]
R5F1017CANA [CX4012]	R5F1017CDNA [CX4012]
R5F1017DANA [CX4012]	R5F1017DDNA [CX4012]
R5F1017EANA [CX4012]	R5F1017EDNA [CX4012]
R5F1017FANA [CX4012]	R5F1017FDNA [CX4012]
R5F1017GANA [CX4012]	R5F1017GDNA [CX4012]
R5F1017HANA [CX4012]	R5F1017HDNA [CX4012]
R5F1017JANA [CX4012]	R5F1017JDNA [CX4012]
R5F1017KANA [CX4012]	R5F1017KDNA [CX4012]
R5F1017LANA [CX4012]	R5F1017LDNA [CX4012]
R5F1018AALA [CX0001]	R5F1018ADLA [CX0001]
R5F1018CALA [CX0001]	R5F1018CDLA [CX0001]
R5F1018DALA [CX0001]	R5F1018DDLA [CX0001]
R5F1018EALA [CX0001]	R5F1018EDLA [CX0001]

R5F1018FALA [CX0001]	R5F1018FDLA [CX0001]
R5F1018GALA [CX0001]	R5F1018GDLA [CX0001]
R5F1018HALA [CX0001]	R5F1018HDLA [CX0001]
R5F1018JALA [CX0001]	R5F1018JDLA [CX0001]
R5F1018KALA [CX0001]	R5F1018KDLA [CX0001]
R5F1018LALA [CX0001]	R5F1018LDLA [CX0001]
R5F101AAASP [CX1026]	R5F101AADSP [CX1026]
R5F101ACASP [CX1026]	R5F101ACDSP [CX1026]
R5F101ADASP [CX1026]	R5F101ADDSP [CX1026]
R5F101AEASP [CX1026]	R5F101AEDSP [CX1026]
R5F101AFASP [CX1026]	R5F101AFDSP [CX1026]
R5F101AGASP [CX1026]	R5F101AGDSP [CX1026]
R5F101AHASP [CX1026]	R5F101AHDSP [CX1026]
R5F101AJASP [CX1026]	R5F101AJDSP [CX1026]
R5F101AKASP [CX1026]	R5F101AKDSP [CX1026]
R5F101ALASP [CX1026]	R5F101ALDSP [CX1026]
R5F101BAANA [CX4015]	R5F101BADNA [CX4015]
R5F101BCANA [CX4015]	R5F101BCDNA [CX4015]
R5F101BDANA [CX4015]	R5F101BDDNA [CX4015]
R5F101BEANA [CX4015]	R5F101BEDNA [CX4015]
R5F101BFANA [CX4015]	R5F101BFDNA [CX4015]
R5F101BGANA [CX4015]	R5F101BGDNA [CX4015]
R5F101BHANA [CX4015]	R5F101BHDNA [CX4015]
R5F101BJANA [CX4015]	R5F101BJDNA [CX4015]
R5F101BKANA [CX4015]	R5F101BKDNA [CX4015]
R5F101BLANA [CX4015]	R5F101BLDNA [CX4015]
R5F101CAALA [CX0001]	R5F101CADLA [CX0001]
R5F101CCALA [CX0001]	R5F101CCDLA [CX0001]
R5F101CDALA [CX0001]	R5F101CDDL A [CX0001]
R5F101CEALA [CX0001]	R5F101CEDLA [CX0001]
R5F101CFALA [CX0001]	R5F101CFDLA [CX0001]
R5F101CGALA [CX0001]	R5F101CGDLA [CX0001]
R5F101CHALA [CX0001]	R5F101CHDLA [CX0001]
R5F101CJALA [CX0001]	R5F101CJDLA [CX0001]
R5F101CKALA [CX0001]	R5F101CKDLA [CX0001]
R5F101CLALA [CX0001]	R5F101CLDLA [CX0001]
R5F101EAANA [CX4017]	R5F101EADNA [CX4017]
R5F101ECANA [CX4017]	R5F101ECDNA [CX4017]
R5F101EDANA [CX4017]	R5F101EDDNA [CX4017]
R5F101EEANA [CX4017]	R5F101EEDNA [CX4017]
R5F101EFANA [CX4017]	R5F101EFDNA [CX4017]
R5F101EGANA [CX4017]	R5F101EGDNA [CX4017]
R5F101EHANA [CX4017]	R5F101EHDNA [CX4017]
R5F101EJANA [CX4017]	R5F101EJDNA [CX4017]
R5F101EKANA [CX4017]	R5F101EKDNA [CX4017]
R5F101ELANA [CX4017]	R5F101ELDNA [CX4017]
R5F101FAAFP [CX3005]	R5F101FADFP [CX3005]
R5F101FCAFP [CX3005]	R5F101FCDFP [CX3005]
R5F101FDAFP [CX3005]	R5F101FDDFP [CX3005]
R5F101FEAFP [CX3005]	R5F101FEDFP [CX3005]
R5F101FFAFP [CX3005]	R5F101FFDFP [CX3005]
R5F101FGAFP [CX3005]	R5F101FGDFP [CX3005]
R5F101FHAFP [CX3005]	R5F101FHDFP [CX3005]
R5F101FJAFP [CX3005]	R5F101FJDFP [CX3005]
R5F101FKAFP [CX3005]	R5F101FKDFP [CX3005]
R5F101FLAFP [CX3005]	R5F101FLDFP [CX3005]
R5F101GAAFB [CX3007]	R5F101GAANA [CX4021]
R5F101GADFB [CX3007]	R5F101GADNA [CX4021]
R5F101GCAFB [CX3007]	R5F101GCANA [CX4021]

R5F101GCDFB [CX3007]	R5F101GCDNA [CX4021]
R5F101GDAFB [CX3007]	R5F101GDANA [CX4021]
R5F101GDDFB [CX3007]	R5F101GDDNA [CX4021]
R5F101GEAFB [CX3007]	R5F101GEANA [CX4021]
R5F101GEDFB [CX3007]	R5F101GEDNA [CX4021]
R5F101GFAFB [CX3007]	R5F101GFANA [CX4021]
R5F101GDFB [CX3007]	R5F101GFDNA [CX4021]
R5F101GGAFB [CX3007]	R5F101GGANA [CX4021]
R5F101GGDFB [CX3007]	R5F101GGDNA [CX4021]
R5F101GHAFB [CX3007]	R5F101GHANA [CX4021]
R5F101GHDFB [CX3007]	R5F101GHDNA [CX4021]
R5F101GJAFB [CX3007]	R5F101GJANA [CX4021]
R5F101GJDFB [CX3007]	R5F101GJDNA [CX4021]
R5F101GKAFB [CX3007]	R5F101GKANA [CX4021]
R5F101GKDFB [CX3007]	R5F101GKDNA [CX4021]
R5F101GLAFB [CX3007]	R5F101GLANA [CX4021]
R5F101GLDFB [CX3007]	R5F101GLDNA [CX4021]
R5F101JCAFA [CX3010]	R5F101JCDFB [CX3010]
R5F101JDAFA [CX3010]	R5F101JDDFA [CX3010]
R5F101JEAFA [CX3010]	R5F101JEDFA [CX3010]
R5F101JFAFA [CX3010]	R5F101JFDFA [CX3010]
R5F101JGAFA [CX3010]	R5F101JGDFA [CX3010]
R5F101JHAFA [CX3010]	R5F101JHDFB [CX3010]
R5F101JJFAFA [CX3010]	R5F101JJDFB [CX3010]
R5F101JKFAFA [CX3010]	R5F101JKDFB [CX3010]
R5F101JLAFA [CX3010]	R5F101JLDFB [CX3010]
R5F101LCABG [CX0001]	R5F101LCAFA [CX3011]
R5F101LCAFB [CX3011]	R5F101LCAFC [CX3011]
R5F101LCDBG [CX0001]	R5F101LCDFA [CX3011]
R5F101LCDFB [CX3011]	R5F101LCDFC [CX3011]
R5F101LDABG [CX0001]	R5F101LDAFA [CX3011]
R5F101LDAFB [CX3011]	R5F101LDAFC [CX3011]
R5F101LDDBG [CX0001]	R5F101LDDFA [CX3011]
R5F101LDDFB [CX3011]	R5F101LDDFC [CX3011]
R5F101LEABG [CX0001]	R5F101LEAFA [CX3011]
R5F101LEAFB [CX3011]	R5F101LEAFC [CX3011]
R5F101LEDBG [CX0001]	R5F101LEDFA [CX3011]
R5F101LEDFB [CX3011]	R5F101LEDFC [CX3011]
R5F101LFABG [CX0001]	R5F101LFAFA [CX3011]
R5F101LFAFB [CX3011]	R5F101LFAFC [CX3011]
R5F101LFDBG [CX0001]	R5F101LFDFA [CX3011]
R5F101LFDDB [CX3011]	R5F101LFDFC [CX3011]
R5F101LGABG [CX0001]	R5F101LGAFB [CX3011]
R5F101LGAFB [CX3011]	R5F101LGAFC [CX3011]
R5F101LGDBG [CX0001]	R5F101LGDFA [CX3011]
R5F101LGDFB [CX3011]	R5F101LGDFC [CX3011]
R5F101LHABG [CX0001]	R5F101LHAFA [CX3011]
R5F101LHAFB [CX3011]	R5F101LHAFC [CX3011]
R5F101LHDBG [CX0001]	R5F101LHDFB [CX3011]
R5F101LHDFB [CX3011]	R5F101LHDFC [CX3011]
R5F101LJABG [CX0001]	R5F101LJAFA [CX3011]
R5F101LJAFB [CX3011]	R5F101LJAFC [CX3011]
R5F101LJDBG [CX0001]	R5F101LJDFB [CX3011]
R5F101LJDFB [CX3011]	R5F101LJDFC [CX3011]
R5F101LKABG [CX0001]	R5F101LKAFB [CX3011]
R5F101LKAFB [CX3011]	R5F101LKAFC [CX3011]
R5F101LKDBG [CX0001]	R5F101LKDFB [CX3011]
R5F101LKDFB [CX3011]	R5F101LKDFC [CX3011]
R5F101LLABG [CX0001]	R5F101LLAFA [CX3011]



R5F101LLAFB [CX3011]	R5F101LLAFC [CX3011]
R5F101LLDBG [CX0001]	R5F101LLDFA [CX3011]
R5F101LLDFB [CX3011]	R5F101LLDFC [CX3011]
R5F101MCAFA [CX3017]	R5F101MCAFB [CX3016]
R5F101MC DFA [CX3017]	R5F101MCDFB [CX3016]
R5F101MDAFA [CX3017]	R5F101MDAFB [CX3016]
R5F101MDDFA [CX3017]	R5F101MDDFB [CX3016]
R5F101MEAFA [CX3017]	R5F101MEAFB [CX3016]
R5F101MEDFA [CX3017]	R5F101MEDFB [CX3016]
R5F101MFAFA [CX3017]	R5F101MFAFB [CX3016]
R5F101MFDFA [CX3017]	R5F101MFDFB [CX3016]
R5F101MG AFA [CX3017]	R5F101MGAFB [CX3016]
R5F101MG DFA [CX3017]	R5F101MGDFB [CX3016]
R5F101MH AFA [CX3017]	R5F101MHAFB [CX3016]
R5F101MH DFA [CX3017]	R5F101MHDFB [CX3016]
R5F101MJ AFA [CX3017]	R5F101MJAFB [CX3016]
R5F101MJ DFA [CX3017]	R5F101MJDFB [CX3016]
R5F101MK AFA [CX3017]	R5F101MKAFB [CX3016]
R5F101MK DFA [CX3017]	R5F101MKDFB [CX3016]
R5F101ML AFA [CX3017]	R5F101MLAFB [CX3016]
R5F101ML DFA [CX3017]	R5F101MLDFB [CX3016]
R5F101PCAFA [CX3062]	R5F101PCA FB [CX3021]
R5F101PC DFA [CX3062]	R5F101PCDFB [CX3021]
R5F101PD AFA [CX3062]	R5F101PDAFB [CX3021]
R5F101PD DFA [CX3062]	R5F101PDDFB [CX3021]
R5F101PE AFA [CX3062]	R5F101PEAFB [CX3021]
R5F101PE DFA [CX3062]	R5F101PEDFB [CX3021]
R5F101PF AFA [CX3062]	R5F101PFAFB [CX3021]
R5F101PF DFA [CX3062]	R5F101PFDFB [CX3021]
R5F101PG AFA [CX3062]	R5F101PGAFB [CX3021]
R5F101PG DFA [CX3062]	R5F101PGDFB [CX3021]
R5F101PH AFA [CX3062]	R5F101PHAFB [CX3021]
R5F101PH DFA [CX3062]	R5F101PHDFB [CX3021]
R5F101PJ AFA [CX3062]	R5F101PJAFB [CX3021]
R5F101PJ DFA [CX3062]	R5F101PJDFB [CX3021]
R5F101PK AFA [CX3062]	R5F101PKAFB [CX3021]
R5F101PK DFA [CX3062]	R5F101PKDFB [CX3021]
R5F101PL AFA [CX3062]	R5F101PLAFB [CX3021]
R5F101PL DFA [CX3062]	R5F101PLDFB [CX3021]
R5F101SC AFB [CX3031]	R5F101SCDFB [CX3031]
R5F101SD AFB [CX3031]	R5F101SDDFB [CX3031]
R5F101SE AFB [CX3031]	R5F101SEDFB [CX3031]
R5F101SF AFB [CX3031]	R5F101SFDFB [CX3031]
R5F101SG AFB [CX3031]	R5F101SGDFB [CX3031]
R5F101SH AFB [CX3031]	R5F101SHDFB [CX3031]
R5F101SJ AFB [CX3031]	R5F101SJDFB [CX3031]
R5F101SK AFB [CX3031]	R5F101SKDFB [CX3031]
R5F101SL AFB [CX3031]	R5F101SLDFB [CX3031]
R5F10266ASP [CX1001]	R5F10266DSP [CX1001]
R5F10267DSP [CX1001]	R5F10268DSP [CX1001]
R5F10269DSP [CX1001]	R5F1026ADSP [CX1001]
R5F10276ANA [CX4012]	R5F10276DNA [CX4012]
R5F10277DNA [CX4012]	R5F10278DNA [CX4012]
R5F10279DNA [CX4012]	R5F1027ADNA [CX4012]
R5F102A6ASP [CX1026]	R5F102A6DSP [CX1026]
R5F102A7DSP [CX1026]	R5F102A8DSP [CX1026]
R5F102A9DSP [CX1026]	R5F102AADSP [CX1026]
R5F10366ASP [CX1001]	R5F10366DSP [CX1001]
R5F10367ASP [CX1001]	R5F10367DSP [CX1001]

R5F10368ASP [CX1001] R5F10368DSP [CX1001]  
R5F10369ASP [CX1001] R5F10369DSP [CX1001]  
R5F1036AASP [CX1001] R5F1036ADSP [CX1001]  
R5F10376ANA [CX4012] R5F10376DNA [CX4012]  
R5F10377ANA [CX4012] R5F10377DNA [CX4012]  
R5F10378ANA [CX4012] R5F10378DNA [CX4012]  
R5F10379ANA [CX4012] R5F10379DNA [CX4012]  
R5F1037AANA [CX4012] R5F1037ADNA [CX4012]  
R5F103A6ASP [CX1026] R5F103A6DSP [CX1026]  
R5F103A7ASP [CX1026] R5F103A7DSP [CX1026]  
R5F103A8ASP [CX1026] R5F103A8DSP [CX1026]  
R5F103A9ASP [CX1026] R5F103A9DSP [CX1026]  
R5F103AAASP [CX1026] R5F103AADSP [CX1026]  
R5F10Y14ASP [CX1001] R5F10Y16ASP [CX1001]  
R5F10Y17ASP [CX1001] R5F10Y44ASP [CX1001]  
R5F10Y46ASP [CX1001] R5F10Y47ASP [CX1001]  
R7F01592ESN [CX1033] R7F01692ESN [CX1033]  
R7F0C011B2001DFP [CX3001] R7F0C012B2001DFP [CX3001]  
R7F0C013B2001DFP [CX3001] R7F0C014 [CX3001]  
uPD70F3003@TQFP100 [CX3043] uPD70F3003A@TQFP100 [CX3043]  
uPD70F3025@TQFP100 [CX3043] uPD70F3025A@TQFP100 [CX3043]  
uPD75P0016@SDIP42 [CX0042] uPD75P0016@TQFP44 [CX3066]  
uPD75P0016CU@SDIP42 [CX0042] uPD75P0016GB@TQFP44 [CX3002]  
uPD75P008CU@SDIP42 [CX0042] uPD75P008GB@TQFP44 [CX3002]  
uPD75P108BCW@SDIP64 [CX0064] uPD75P108BDW [CX0064]  
uPD75P108BGF@PQFP64 [CX3015] uPD75P108CW@SDIP64 [CX0064]  
uPD75P108DW [CX0064] uPD75P108GF@PQFP64 [CX3015]  
uPD75P116BCW [CX0064] uPD75P116BDW [CX0064]  
uPD75P116BGF [CX3015] uPD75P116CW@SDIP64 [CX0064]  
uPD75P116DW [CX0064] uPD75P116GF@PQFP64 [CX3015]  
uPD75P218CW@PQFP64 [CX3015] uPD75P218CW@SDIP64 [CX0064]  
uPD75P308AGF@PQFP80 [CX3019] uPD75P308BGC@PQFP80 [CX3018]  
uPD75P308BGK@PQFP80 [CX3016] uPD75P308GC [CX3018]  
uPD75P308GF@PQFP80 [CX3019] uPD75P308GK [CX3016]  
uPD75P316AGF@PQFP80 [CX3019] uPD75P316BGC@PQFP80 [CX3018]  
uPD75P316BGK@PQFP80 [CX3016] uPD75P316GC [CX3018]  
uPD75P316GF@PQFP80 [CX3019] uPD75P316GK [CX3016]  
uPD75P54CS [CX0001] uPD75P54G@SOP20 [CX1026]  
uPD75P64CS [CX0001] uPD75P64G@SOP20 [CX1026]  
uPD78CP18CW [CX0064] uPD78CP18CW(A) [CX0064]  
uPD78CP18CW(B) [CX0064] uPD78CP18DW [CX0064]  
uPD78CP18DW(A) [CX0064] uPD78CP18DW(B) [CX0064]  
uPD78CP18GQ [CX0065] uPD78CP18GQ(A) [CX0065]  
uPD78CP18GQ(B) [CX0065] uPD78F0101HMC(A)@SSOP30 [CX1027]  
uPD78F0101HMC(A1)@SSOP30 [CX1027] uPD78F0102HMC(A)@SSOP30 [CX1027]  
uPD78F0101HMC@SSOP30 [CX1027] uPD78F0103HMC(A)@SSOP30 [CX1027]  
uPD78F0102HMC(A1)@SSOP30 [CX1027] uPD78F0103HMC@SSOP30 [CX1027]  
uPD78F0102HMC@SSOP30 [CX1027] uPD78F0103M1MC@SSOP30 [CX1027]  
uPD78F0103HMC(A1)@SSOP30 [CX1027] uPD78F0103M1MCA1@SSOP30 [CX1027]  
uPD78F0103M1MCA@SSOP30 [CX1027] uPD78F0103M2MCA@SSOP30 [CX1027]  
uPD78F0103M2MC@SSOP30 [CX1027] uPD78F0103M3MC@SSOP30 [CX1027]  
uPD78F0103M2MCA1@SSOP30 [CX1027] uPD78F0103M3MCA1@SSOP30 [CX1027]  
uPD78F0103M3MCA@SSOP30 [CX1027] uPD78F0103M4MCA@SSOP30 [CX1027]  
uPD78F0103M4MC@SSOP30 [CX1027] uPD78F0103M5MC@SSOP30 [CX1027]  
uPD78F0103M4MCA1@SSOP30 [CX1027] uPD78F0103M5MCA1@SSOP30 [CX1027]  
uPD78F0103M5MCA@SSOP30 [CX1027] uPD78F0103M6MCA@SSOP30 [CX1027]  
uPD78F0103M6MC@SSOP30 [CX1027] uPD78F0103N1MC@QFP64 [CX3011]  
uPD78F0103M6MCA1@SSOP30 [CX1027]

uPD78F0103N1MCA@QFP64 [CX3011]  
uPD78F0103N2MC@QFP64 [CX3011]  
uPD78F0103N2MCA1@QFP64 [CX3011]  
uPD78F0103N3MCA@QFP64 [CX3011]  
uPD78F0103N4MC@QFP64 [CX3011]  
uPD78F0103N4MCA1@QFP64 [CX3011]  
uPD78F0103N5MCA@QFP64 [CX3011]  
uPD78F0103N6MC@QFP64 [CX3011]  
uPD78F0103N6MCA1@QFP64 [CX3011]  
uPD78F0112HGB(A1)@QFP44 [CX3003]  
uPD78F0112HGB(A)@QFP44 [CX3003]  
uPD78F0113HGB@QFP44 [CX3003]  
uPD78F0114HDGB(A1)@QFP44 [CX3003]  
uPD78F0114HDGB(A)@QFP44 [CX3003]  
uPD78F0114HGB(A1)@QFP44 [CX3003]  
uPD78F0114M1GB(A)@QFP44 [CX3003]  
uPD78F0114M1GB(A1)@QFP44 [CX3003]  
uPD78F0114M1GB@QFP44 [CX3003]  
uPD78F0114M2GB(A1)@QFP44 [CX3003]  
uPD78F0114M2GB@QFP44 [CX3003]  
uPD78F0114M3GB(A1)@QFP44 [CX3003]  
uPD78F0114M3GB@QFP44 [CX3003]  
uPD78F0114M4GB(A1)@QFP44 [CX3003]  
uPD78F0114M4GB@QFP44 [CX3003]  
uPD78F0114M5GB(A1)@QFP44 [CX3003]  
uPD78F0114M5GB@QFP44 [CX3003]  
uPD78F0114M6GB(A1)@QFP44 [CX3003]  
uPD78F0114M6GB@QFP44 [CX3003]  
uPD78F0118M1GB(A1)@QFP44 [CX3003]  
uPD78F0118M1GB@QFP44 [CX3003]  
uPD78F0118M2GB(A1)@QFP44 [CX3003]  
uPD78F0118M2GB@QFP44 [CX3003]  
uPD78F0118M3GB(A1)@QFP44 [CX3003]  
uPD78F0118M3GB@QFP44 [CX3003]  
uPD78F0118M4GB(A1)@QFP44 [CX3003]  
uPD78F0118M4GB@QFP44 [CX3003]  
uPD78F0118M5GB(A1)@QFP44 [CX3003]  
uPD78F0118M5GB@QFP44 [CX3003]  
uPD78F0118M6GB(A1)@QFP44 [CX3003]  
uPD78F0118M6GB@QFP44 [CX3003]  
uPD78F0122HGB(A1)@QFP52 [CX3010]  
uPD78F0123HGB(A)@QFP52 [CX3010]  
uPD78F0123HGB@QFP52 [CX3010]  
uPD78F0124HDGB(A1)@QFP52 [CX3010]  
uPD78F0124HDGB@QFP52 [CX3010]  
uPD78F0124HGB(A1)@QFP52 [CX3010]  
uPD78F0132HGB(A)@QFP64 [CX3011]  
uPD78F0132HGB@QFP64 [CX3011]  
uPD78F0132HGC(A1)@QFP64 [CX3013]  
uPD78F0132HGC(A)@QFP64 [CX3012]  
uPD78F0132HGK@QFP64 [CX3012]  
uPD78F0133HGB(A1)@QFP64 [CX3011]  
uPD78F0133HGC(A)@QFP64 [CX3013]  
uPD78F0133HGC@QFP64 [CX3013]  
uPD78F0133HGK(A1)@QFP64 [CX3012]  
uPD78F0134HGB(A)@QFP64 [CX3011]  
uPD78F0134HGB@QFP64 [CX3011]  
uPD78F0134HGC(A1)@QFP64 [CX3013]  
uPD78F0134HGK(A)@QFP64 [CX3012]

uPD78F0103N1MCA1@QFP64 [CX3011]  
uPD78F0103N2MCA@QFP64 [CX3011]  
uPD78F0103N3MC@QFP64 [CX3011]  
uPD78F0103N3MCA1@QFP64 [CX3011]  
uPD78F0103N4MCA@QFP64 [CX3011]  
uPD78F0103N5MC@QFP64 [CX3011]  
uPD78F0103N5MCA1@QFP64 [CX3011]  
uPD78F0103N6MCA@QFP64 [CX3011]  
uPD78F0112HGB(A)@QFP44 [CX3003]  
uPD78F0112HGB@QFP44 [CX3003]  
uPD78F0113HGB(A1)@QFP44 [CX3003]  
uPD78F0114HDGB(A)@QFP44 [CX3003]  
  
uPD78F0114HGB(A)@QFP44 [CX3003]  
uPD78F0114HGB@QFP44 [CX3003]  
  
uPD78F0114M2GB(A)@QFP44 [CX3003]  
uPD78F0114M3GB(A)@QFP44 [CX3003]  
uPD78F0114M4GB(A)@QFP44 [CX3003]  
uPD78F0114M5GB(A)@QFP44 [CX3003]  
uPD78F0114M6GB(A)@QFP44 [CX3003]  
uPD78F0118M1GB(A)@QFP44 [CX3003]  
uPD78F0118M2GB(A)@QFP44 [CX3003]  
uPD78F0118M3GB(A)@QFP44 [CX3003]  
uPD78F0118M4GB(A)@QFP44 [CX3003]  
uPD78F0118M5GB(A)@QFP44 [CX3003]  
uPD78F0118M6GB(A)@QFP44 [CX3003]  
uPD78F0122HGB(A)@QFP52 [CX3010]  
uPD78F0122HGB@QFP52 [CX3010]  
uPD78F0123HGB(A1)@QFP52 [CX3010]  
uPD78F0124HDGB(A)@QFP52 [CX3010]  
uPD78F0124HGB(A)@QFP52 [CX3010]  
uPD78F0124HGB@QFP52 [CX3010]  
uPD78F0132HGB(A1)@QFP64 [CX3011]  
uPD78F0132HGC(A)@QFP64 [CX3013]  
uPD78F0132HGC@QFP64 [CX3013]  
uPD78F0132HGK(A1)@QFP64 [CX3012]  
uPD78F0133HGB(A)@QFP64 [CX3011]  
uPD78F0133HGB@QFP64 [CX3011]  
uPD78F0133HGC(A1)@QFP64 [CX3013]  
uPD78F0133HGK(A)@QFP64 [CX3012]  
uPD78F0133HGK@QFP64 [CX3012]  
uPD78F0134HGB(A1)@QFP64 [CX3011]  
uPD78F0134HGC(A)@QFP64 [CX3013]  
uPD78F0134HGC@QFP64 [CX3013]  
uPD78F0134HGK(A1)@QFP64 [CX3012]

uPD78F0134HGK@QFP64 [CX3012]  
uPD78F0134M1GB\_A@LQFP64 [CX3011]  
uPD78F0134M1GBA1@LQFP64 [CX3011]  
uPD78F0134M1GC\_A@LQFP64 [CX3013]  
uPD78F0134M1GCA1@LQFP64 [CX3013]  
uPD78F0134M1GK\_A@TQFP64 [CX3012]  
uPD78F0134M1GKA1@TQFP64 [CX3012]  
uPD78F0134M2GB\_A@LQFP64 [CX3011]  
uPD78F0134M2GC@LQFP64 [CX3013]  
uPD78F0134M2GCA@LQFP64 [CX3013]  
uPD78F0134M2GK@TQFP64 [CX3012]  
uPD78F0134M2GKA@TQFP64 [CX3012]  
uPD78F0134M3GB@LQFP64 [CX3011]  
uPD78F0134M3GBA@LQFP64 [CX3011]  
uPD78F0134M3GC@LQFP64 [CX3013]  
uPD78F0134M3GCA@LQFP64 [CX3013]  
uPD78F0134M3GK@TQFP64 [CX3012]  
uPD78F0134M3GKA@TQFP64 [CX3012]  
uPD78F0134M4GB@LQFP64 [CX3011]  
uPD78F0134M4GBA@LQFP64 [CX3011]  
uPD78F0134M4GC@LQFP64 [CX3013]  
uPD78F0134M4GCA@LQFP64 [CX3013]  
uPD78F0134M4GK@TQFP64 [CX3012]  
uPD78F0134M4GKA@TQFP64 [CX3012]  
uPD78F0134M5GB@LQFP64 [CX3011]  
uPD78F0134M5GBA@LQFP64 [CX3011]  
uPD78F0134M5GC@LQFP64 [CX3013]  
uPD78F0134M5GCA@LQFP64 [CX3013]  
uPD78F0134M5GK@TQFP64 [CX3012]  
uPD78F0134M5GKA@TQFP64 [CX3012]  
uPD78F0134M6GB@LQFP64 [CX3011]  
uPD78F0134M6GBA@LQFP64 [CX3011]  
uPD78F0134M6GC@LQFP64 [CX3013]  
uPD78F0134M6GCA@LQFP64 [CX3013]  
uPD78F0134M6GK@TQFP64 [CX3012]  
uPD78F0134M6GKA@TQFP64 [CX3012]  
uPD78F0136HGB(A)@QFP64 [CX3011]  
uPD78F0136HGB@QFP64 [CX3011]  
uPD78F0136HGC(A1)@QFP64 [CX3013]  
uPD78F0136HGK(A)@QFP64 [CX3012]  
uPD78F0136HGK@QFP64 [CX3012]  
uPD78F0138HDGB(A1)@QFP64 [CX3011]  
uPD78F0138HDGB@QFP64 [CX3011]  
uPD78F0138HDGC(A1)@QFP64 [CX3013]  
uPD78F0138HDGC@QFP64 [CX3013]  
uPD78F0138HDGK(A1)@QFP64 [CX3012]  
uPD78F0138HDGK@QFP64 [CX3012]  
uPD78F0138HGB(A1)@QFP64 [CX3011]  
uPD78F0138HGC(A)@QFP64 [CX3013]  
uPD78F0138HGC@QFP64 [CX3013]  
uPD78F0138HGK(A1)@QFP64 [CX3012]  
uPD78F0138M1GB@LQFP64 [CX3011]  
uPD78F0138M1GBA@LQFP64 [CX3011]  
uPD78F0138M1GC@LQFP64 [CX3013]  
uPD78F0138M1GCA@LQFP64 [CX3013]  
uPD78F0138M1GK@TQFP64 [CX3012]  
uPD78F0138M1GKA@TQFP64 [CX3012]  
uPD78F0138M2GB@LQFP64 [CX3011]  
uPD78F0138M2GBA@LQFP64 [CX3011]

uPD78F0134M1GB@LQFP64 [CX3011]  
uPD78F0134M1GBA@LQFP64 [CX3011]  
uPD78F0134M1GC@LQFP64 [CX3013]  
uPD78F0134M1GCA@LQFP64 [CX3013]  
uPD78F0134M1GK@TQFP64 [CX3012]  
uPD78F0134M1GKA@TQFP64 [CX3012]  
uPD78F0134M2GB@LQFP64 [CX3011]  
uPD78F0134M2GBA@LQFP64 [CX3011]  
uPD78F0134M2GC\_A@LQFP64 [CX3013]  
uPD78F0134M2GCA1@LQFP64 [CX3013]  
uPD78F0134M2GK\_A@TQFP64 [CX3012]  
uPD78F0134M2GKA1@TQFP64 [CX3012]  
uPD78F0134M3GB\_A@LQFP64 [CX3011]  
uPD78F0134M3GBA1@LQFP64 [CX3011]  
uPD78F0134M3GC\_A@LQFP64 [CX3013]  
uPD78F0134M3GCA1@LQFP64 [CX3013]  
uPD78F0134M3GK\_A@TQFP64 [CX3012]  
uPD78F0134M3GKA1@TQFP64 [CX3012]  
uPD78F0134M4GB\_A@LQFP64 [CX3011]  
uPD78F0134M4GBA1@LQFP64 [CX3011]  
uPD78F0134M4GC\_A@LQFP64 [CX3013]  
uPD78F0134M4GCA1@LQFP64 [CX3013]  
uPD78F0134M4GK\_A@TQFP64 [CX3012]  
uPD78F0134M4GKA1@TQFP64 [CX3012]  
uPD78F0134M5GB\_A@LQFP64 [CX3011]  
uPD78F0134M5GBA1@LQFP64 [CX3011]  
uPD78F0134M5GC\_A@LQFP64 [CX3013]  
uPD78F0134M5GCA1@LQFP64 [CX3013]  
uPD78F0134M5GK\_A@TQFP64 [CX3012]  
uPD78F0134M5GKA1@TQFP64 [CX3012]  
uPD78F0134M6GB\_A@LQFP64 [CX3011]  
uPD78F0134M6GBA1@LQFP64 [CX3011]  
uPD78F0134M6GC\_A@LQFP64 [CX3013]  
uPD78F0134M6GCA1@LQFP64 [CX3013]  
uPD78F0134M6GK\_A@TQFP64 [CX3012]  
uPD78F0134M6GKA1@TQFP64 [CX3012]  
uPD78F0136HGB(A1)@QFP64 [CX3011]  
uPD78F0136HGC(A)@QFP64 [CX3013]  
uPD78F0136HGC@QFP64 [CX3013]  
uPD78F0136HGK(A1)@QFP64 [CX3012]  
uPD78F0138HDGB(A)@QFP64 [CX3011]  
uPD78F0138HDGC(A)@QFP64 [CX3013]  
uPD78F0138HDGK(A)@QFP64 [CX3012]  
uPD78F0138HGB(A)@QFP64 [CX3011]  
uPD78F0138HGB@QFP64 [CX3011]  
uPD78F0138HGC(A1)@QFP64 [CX3013]  
uPD78F0138HGK(A)@QFP64 [CX3012]  
uPD78F0138HGK@QFP64 [CX3012]  
uPD78F0138M1GB\_A@LQFP64 [CX3011]  
uPD78F0138M1GBA1@LQFP64 [CX3011]  
uPD78F0138M1GC\_A@LQFP64 [CX3013]  
uPD78F0138M1GCA1@LQFP64 [CX3013]  
uPD78F0138M1GK\_A@TQFP64 [CX3012]  
uPD78F0138M1GKA1@TQFP64 [CX3012]  
uPD78F0138M2GB\_A@LQFP64 [CX3011]  
uPD78F0138M2GBA1@LQFP64 [CX3011]

uPD78F0138M2GC@LQFP64 [CX3013]  
uPD78F0138M2GCA@LQFP64 [CX3013]  
uPD78F0138M2GK@TQFP64 [CX3012]  
uPD78F0138M2GKA@TQFP64 [CX3012]  
uPD78F0138M3GB@LQFP64 [CX3011]  
uPD78F0138M3GBA@LQFP64 [CX3011]  
uPD78F0138M3GC@LQFP64 [CX3013]  
uPD78F0138M3GCA@LQFP64 [CX3013]  
uPD78F0138M3GK@TQFP64 [CX3012]  
uPD78F0138M3GKA@TQFP64 [CX3012]  
uPD78F0138M4GB@LQFP64 [CX3011]  
uPD78F0138M4GBA@LQFP64 [CX3011]  
uPD78F0138M4GC@LQFP64 [CX3013]  
uPD78F0138M4GCA@LQFP64 [CX3013]  
uPD78F0138M4GK@TQFP64 [CX3012]  
uPD78F0138M4GKA@TQFP64 [CX3012]  
uPD78F0138M5GB@LQFP64 [CX3011]  
uPD78F0138M5GBA@LQFP64 [CX3011]  
uPD78F0138M5GC@LQFP64 [CX3013]  
uPD78F0138M5GCA@LQFP64 [CX3013]  
uPD78F0138M5GK@TQFP64 [CX3012]  
uPD78F0138M5GKA@TQFP64 [CX3012]  
uPD78F0138M6GB@LQFP64 [CX3011]  
uPD78F0138M6GBA@LQFP64 [CX3011]  
uPD78F0138M6GC@LQFP64 [CX3013]  
uPD78F0138M6GCA@LQFP64 [CX3013]  
uPD78F0138M6GK@TQFP64 [CX3012]  
uPD78F0138M6GKA@TQFP64 [CX3012]  
uPD78F0138M2GBA@LQFP64 [CX3011]  
uPD78F0148M1GC(A1)@QFP80 [CX3018]  
uPD78F0148M1GC@QFP80 [CX3018]  
uPD78F0148M1GK(A1)@QFP80 [CX3016]  
uPD78F0148M1GK@QFP80 [CX3016]  
uPD78F0148M2GC(A1)@QFP80 [CX3018]  
uPD78F0148M2GC@QFP80 [CX3018]  
uPD78F0148M2GK(A1)@QFP80 [CX3016]  
uPD78F0148M2GK@QFP80 [CX3016]  
uPD78F0148M3GC(A1)@QFP80 [CX3018]  
uPD78F0148M3GC@QFP80 [CX3018]  
uPD78F0148M3GK(A1)@QFP80 [CX3016]  
uPD78F0148M3GK@QFP80 [CX3016]  
uPD78F0148M4GC(A1)@QFP80 [CX3018]  
uPD78F0148M4GC@QFP80 [CX3018]  
uPD78F0148M4GK(A1)@QFP80 [CX3016]  
uPD78F0148M4GK@QFP80 [CX3016]  
uPD78F0148M5GC(A1)@QFP80 [CX3018]  
uPD78F0148M5GC@QFP80 [CX3018]  
uPD78F0148M5GK(A1)@QFP80 [CX3016]  
uPD78F0148M5GK@QFP80 [CX3016]  
uPD78F0148M6GC(A1)@QFP80 [CX3018]  
uPD78F0148M6GC@QFP80 [CX3018]  
uPD78F0148M6GK(A1)@QFP80 [CX3016]  
uPD78F0148M6GK@QFP80 [CX3016]  
uPD78F0361AGK [CX3012]  
uPD78F0361GK [CX3012]  
uPD78F0362AGK [CX3012]  
uPD78F0362GK [CX3012]  
uPD78F0363ADGK [CX3012]  
uPD78F0363AGK [CX3012]

uPD78F0138M2GC\_A@LQFP64 [CX3013]  
uPD78F0138M2GCA1@LQFP64 [CX3013]  
uPD78F0138M2GK\_A@TQFP64 [CX3012]  
uPD78F0138M2GKA1@TQFP64 [CX3012]  
uPD78F0138M3GB\_A@LQFP64 [CX3011]  
uPD78F0138M3GBA1@LQFP64 [CX3011]  
uPD78F0138M3GC\_A@LQFP64 [CX3013]  
uPD78F0138M3GCA1@LQFP64 [CX3013]  
uPD78F0138M3GK\_A@TQFP64 [CX3012]  
uPD78F0138M3GKA1@TQFP64 [CX3012]  
uPD78F0138M4GB\_A@LQFP64 [CX3011]  
uPD78F0138M4GBA1@LQFP64 [CX3011]  
uPD78F0138M4GC\_A@LQFP64 [CX3013]  
uPD78F0138M4GCA1@LQFP64 [CX3013]  
uPD78F0138M4GK\_A@TQFP64 [CX3012]  
uPD78F0138M4GKA1@TQFP64 [CX3012]  
uPD78F0138M5GB\_A@LQFP64 [CX3011]  
uPD78F0138M5GBA1@LQFP64 [CX3011]  
uPD78F0138M5GC\_A@LQFP64 [CX3013]  
uPD78F0138M5GCA1@LQFP64 [CX3013]  
uPD78F0138M5GK\_A@TQFP64 [CX3012]  
uPD78F0138M5GKA1@TQFP64 [CX3012]  
uPD78F0138M6GB\_A@LQFP64 [CX3011]  
uPD78F0138M6GBA1@LQFP64 [CX3011]  
uPD78F0138M6GC\_A@LQFP64 [CX3013]  
uPD78F0138M6GCA1@LQFP64 [CX3013]  
uPD78F0138M6GK\_A@TQFP64 [CX3012]  
uPD78F0138M6GKA1@TQFP64 [CX3012]  
uPD78F0148M1GC(A)@QFP80 [CX3018]  
uPD78F0148M1GK(A)@QFP80 [CX3016]  
uPD78F0148M2GC(A)@QFP80 [CX3018]  
uPD78F0148M2GK(A)@QFP80 [CX3016]  
uPD78F0148M3GC(A)@QFP80 [CX3018]  
uPD78F0148M3GK(A)@QFP80 [CX3016]  
uPD78F0148M4GC(A)@QFP80 [CX3018]  
uPD78F0148M4GK(A)@QFP80 [CX3016]  
uPD78F0148M5GC(A)@QFP80 [CX3018]  
uPD78F0148M5GK(A)@QFP80 [CX3016]  
uPD78F0148M6GC(A)@QFP80 [CX3018]  
uPD78F0148M6GK(A)@QFP80 [CX3016]  
uPD78F0361AGB [CX3011]  
uPD78F0361GB [CX3011]  
uPD78F0362AGB [CX3011]  
uPD78F0362GB [CX3011]  
uPD78F0363ADGB [CX3011]  
uPD78F0363AGB [CX3011]  
uPD78F0363DGB [CX3011]

uPD78F0363DGK [CX3012] uPD78F0363GB [CX3011]  
uPD78F0363GK [CX3012] uPD78F0364AGB [CX3011]  
uPD78F0364AGK [CX3012] uPD78F0364GB [CX3011]  
uPD78F0364GK [CX3012] uPD78F0365AGB [CX3011]  
uPD78F0365AGK [CX3012] uPD78F0365GB [CX3011]  
uPD78F0365GK [CX3012] uPD78F0366AGB [CX3011]  
uPD78F0366AGK [CX3012] uPD78F0366GB [CX3011]  
uPD78F0366GK [CX3012] uPD78F0367ADGB [CX3011]  
uPD78F0367ADGK [CX3012] uPD78F0367AGB [CX3011]  
uPD78F0367AGK [CX3012] uPD78F0367DGB [CX3011]  
uPD78F0367DGK [CX3012] uPD78F0367GB [CX3011]  
uPD78F0367GK [CX3012] uPD78F0371AGC [CX3017]  
uPD78F0371AGK [CX3016] uPD78F0371GC [CX3017]  
uPD78F0371GK [CX3016] uPD78F0372AGC [CX3017]  
uPD78F0372AGK [CX3016] uPD78F0372GC [CX3017]  
uPD78F0372GK [CX3016] uPD78F0373ADGC [CX3017]  
uPD78F0373ADGK [CX3016] uPD78F0373AGC [CX3017]  
uPD78F0373AGK [CX3016] uPD78F0373DGC [CX3017]  
uPD78F0373DGK [CX3016] uPD78F0373GC [CX3017]  
uPD78F0373GK [CX3016] uPD78F0374AGC [CX3017]  
uPD78F0374AGK [CX3016] uPD78F0374GC [CX3017]  
uPD78F0374GK [CX3016] uPD78F0375AGC [CX3017]  
uPD78F0375AGK [CX3016] uPD78F0375GC [CX3017]  
uPD78F0375GK [CX3016] uPD78F0376ADGC [CX3017]  
uPD78F0376ADGK [CX3016] uPD78F0376AGC [CX3017]  
uPD78F0376AGK [CX3016] uPD78F0376DGC [CX3017]  
uPD78F0376DGK [CX3016] uPD78F0376GC [CX3017]  
uPD78F0376GK [CX3016] uPD78F0377ADGC [CX3017]  
uPD78F0377ADGK [CX3016] uPD78F0377AGC [CX3017]  
uPD78F0377AGK [CX3016] uPD78F0377DGC [CX3017]  
uPD78F0377DGK [CX3016] uPD78F0377GC [CX3017]  
uPD78F0377GK [CX3016] uPD78F0381AGC [CX3017]  
uPD78F0381AGK [CX3016] uPD78F0381GC [CX3017]  
uPD78F0381GK [CX3016] uPD78F0382AGC [CX3017]  
uPD78F0382AGK [CX3016] uPD78F0382GC [CX3017]  
uPD78F0382GK [CX3016] uPD78F0383ADGC [CX3017]  
uPD78F0383ADGK [CX3016] uPD78F0383AGC [CX3017]  
uPD78F0383AGK [CX3016] uPD78F0383DGC [CX3017]  
uPD78F0383DGK [CX3016] uPD78F0383GC [CX3017]  
uPD78F0383GK [CX3016] uPD78F0384AGC [CX3017]  
uPD78F0384AGK [CX3016] uPD78F0384GC [CX3017]  
uPD78F0384GK [CX3016] uPD78F0385AGC [CX3017]  
uPD78F0385AGK [CX3016] uPD78F0385GC [CX3017]  
uPD78F0385GK [CX3016] uPD78F0386ADGC [CX3017]  
uPD78F0386ADGK [CX3016] uPD78F0386AGC [CX3017]  
uPD78F0386AGK [CX3016] uPD78F0386DGC [CX3017]  
uPD78F0386DGK [CX3016] uPD78F0386GC [CX3017]  
uPD78F0386GK [CX3016] uPD78F0387ADGC [CX3017]  
uPD78F0387ADGK [CX3016] uPD78F0387AGC [CX3017]  
uPD78F0387AGK [CX3016] uPD78F0387DGC [CX3017]  
uPD78F0387DGK [CX3016] uPD78F0387GC [CX3017]  
uPD78F0387GK [CX3016] uPD78F0391AGC [CX3043]  
uPD78F0391GC [CX3043] uPD78F0392AGC [CX3043]  
uPD78F0392GC [CX3043] uPD78F0393ADGC [CX3043]  
uPD78F0393AGC [CX3043] uPD78F0393DGC [CX3043]  
uPD78F0393GC [CX3043] uPD78F0394AGC [CX3043]  
uPD78F0394GC [CX3043] uPD78F0395AGC [CX3043]  
uPD78F0395GC [CX3043] uPD78F0396ADGC [CX3043]  
uPD78F0396AGC [CX3043] uPD78F0396DGC [CX3043]

uPD78F0396GC [CX3043]  
uPD78F0397AGC [CX3043]  
uPD78F0397GC [CX3043]  
uPD78F0401GA@LQFP48 [CX3047]  
uPD78F0403GA@LQFP48 [CX3047]  
uPD78F0405GA@LQFP48 [CX3047]  
uPD78F0411GA@LQFP48 [CX3047]  
uPD78F0413GA@LQFP48 [CX3047]  
uPD78F0415GA@LQFP48 [CX3047]  
uPD78F0421GB@LQFP52 [CX3010]  
uPD78F0423GB@LQFP52 [CX3010]  
uPD78F0425GB@LQFP52 [CX3010]  
uPD78F0431GB@LQFP52 [CX3010]  
uPD78F0433GB@LQFP52 [CX3010]  
uPD78F0435GB@LQFP52 [CX3010]  
uPD78F0440GK@LQFP64 [CX3012]  
uPD78F0441GK@LQFP64 [CX3012]  
uPD78F0442GK@LQFP64 [CX3012]  
uPD78F0443GK@LQFP64 [CX3012]  
uPD78F0444GK@LQFP64 [CX3012]  
uPD78F0445GK@LQFP64 [CX3012]  
uPD78F0450GK@LQFP64 [CX3012]  
uPD78F0451GK@LQFP64 [CX3012]  
uPD78F0452GK@LQFP64 [CX3012]  
uPD78F0453GK@LQFP64 [CX3012]  
uPD78F0454GK@LQFP64 [CX3012]  
uPD78F0455GK@LQFP64 [CX3012]  
uPD78F0460GK@LQFP64 [CX3012]  
uPD78F0461GK@LQFP64 [CX3012]  
uPD78F0462GK@LQFP64 [CX3012]  
uPD78F0463GK@LQFP64 [CX3012]  
uPD78F0464GK@LQFP64 [CX3012]  
uPD78F0465GK@LQFP64 [CX3012]  
uPD78F0470GK@LQFP80 [CX3016]  
uPD78F0471GK@LQFP80 [CX3016]  
uPD78F0472GK@LQFP80 [CX3016]  
uPD78F0473GK@LQFP80 [CX3016]  
uPD78F0474GK@LQFP80 [CX3016]  
uPD78F0475GK@LQFP80 [CX3016]  
uPD78F0480GK@LQFP80 [CX3016]  
uPD78F0481GK@LQFP80 [CX3016]  
uPD78F0482GK@LQFP80 [CX3016]  
uPD78F0483GK@LQFP80 [CX3016]  
uPD78F0484GK@LQFP80 [CX3016]  
uPD78F0485GK@LQFP80 [CX3016]  
uPD78F0490GK@LQFP80 [CX3016]  
uPD78F0491GK@LQFP80 [CX3016]  
uPD78F0492GK@LQFP80 [CX3016]  
uPD78F0493GK@LQFP80 [CX3016]  
uPD78F0494GK@LQFP80 [CX3016]  
uPD78F0495GK@LQFP80 [CX3016]  
uPD78F0500AAQSA [CX1027]  
uPD78F0500AMC(A)@SSOP30 [CX1027]  
uPD78F0500AQS [CX1027]  
uPD78F0500FC@FLGA36  
uPD78F0500MC@SSOP30 [CX1027]  
uPD78F0501AAQSA [CX1027]  
uPD78F0501AMC(A)@SSOP30 [CX1027]  
uPD78F0501AQS [CX1027]

uPD78F0397ADGC [CX3043]  
uPD78F0397DGC [CX3043]  
uPD78F0400GA@LQFP48 [CX3047]  
uPD78F0402GA@LQFP48 [CX3047]  
uPD78F0404GA@LQFP48 [CX3047]  
uPD78F0410GA@LQFP48 [CX3047]  
uPD78F0412GA@LQFP48 [CX3047]  
uPD78F0414GA@LQFP48 [CX3047]  
uPD78F0420GB@LQFP52 [CX3010]  
uPD78F0422GB@LQFP52 [CX3010]  
uPD78F0424GB@LQFP52 [CX3010]  
uPD78F0430GB@LQFP52 [CX3010]  
uPD78F0432GB@LQFP52 [CX3010]  
uPD78F0434GB@LQFP52 [CX3010]  
uPD78F0440GB@LQFP64 [CX3011]  
uPD78F0441GB@LQFP64 [CX3011]  
uPD78F0442GB@LQFP64 [CX3011]  
uPD78F0443GB@LQFP64 [CX3011]  
uPD78F0444GB@LQFP64 [CX3011]  
uPD78F0445GB@LQFP64 [CX3011]  
uPD78F0450GB@LQFP64 [CX3011]  
uPD78F0451GB@LQFP64 [CX3011]  
uPD78F0452GB@LQFP64 [CX3011]  
uPD78F0453GB@LQFP64 [CX3011]  
uPD78F0454GB@LQFP64 [CX3011]  
uPD78F0455GB@LQFP64 [CX3011]  
uPD78F0460GB@LQFP64 [CX3011]  
uPD78F0461GB@LQFP64 [CX3011]  
uPD78F0462GB@LQFP64 [CX3011]  
uPD78F0463GB@LQFP64 [CX3011]  
uPD78F0464GB@LQFP64 [CX3011]  
uPD78F0465GB@LQFP64 [CX3011]  
uPD78F0470GC@LQFP80 [CX3017]  
uPD78F0471GC@LQFP80 [CX3017]  
uPD78F0472GC@LQFP80 [CX3017]  
uPD78F0473GC@LQFP80 [CX3017]  
uPD78F0474GC@LQFP80 [CX3017]  
uPD78F0475GC@LQFP80 [CX3017]  
uPD78F0480GC@LQFP80 [CX3017]  
uPD78F0481GC@LQFP80 [CX3017]  
uPD78F0482GC@LQFP80 [CX3017]  
uPD78F0483GC@LQFP80 [CX3017]  
uPD78F0484GC@LQFP80 [CX3017]  
uPD78F0485GC@LQFP80 [CX3017]  
uPD78F0490GC@LQFP80 [CX3017]  
uPD78F0491GC@LQFP80 [CX3017]  
uPD78F0492GC@LQFP80 [CX3017]  
uPD78F0493GC@LQFP80 [CX3017]  
uPD78F0494GC@LQFP80 [CX3017]  
uPD78F0495GC@LQFP80 [CX3017]  
uPD78F0500AAQS [CX1027]  
uPD78F0500AFC@FLGA36  
uPD78F0500AMC@SSOP30 [CX1027]  
uPD78F0500AQSA [CX1027]  
uPD78F0500MC(A)@SSOP30 [CX1027]  
uPD78F0501AAQS [CX1027]  
uPD78F0501AFC@FLGA36  
uPD78F0501AMC@SSOP30 [CX1027]  
uPD78F0501AQSA [CX1027]

uPD78F0501FC@FLGA36  
uPD78F0501MC@SSOP30 [CX1027]  
uPD78F0502AAQSA [CX1027]  
uPD78F0502AMC(A)@SSOP30 [CX1027]  
uPD78F0502AQS [CX1027]  
uPD78F0502FC@FLGA36  
uPD78F0502MC@SSOP30 [CX1027]  
uPD78F0503AAQSA [CX1027]  
uPD78F0503ADMC(A)@SSOP30 [CX1027]  
uPD78F0503ADMC@SSOP30 [CX1027]  
uPD78F0503AMC(A)@SSOP30 [CX1027]  
uPD78F0503AQS [CX1027]  
uPD78F0503DFC@FLGA36  
uPD78F0503DMC@SSOP30 [CX1027]  
uPD78F0503MC(A)@SSOP30 [CX1027]  
uPD78F0511AGA(A)@TQFP48 [CX3047]  
uPD78F0511AGA(A2)@TQFP48 [CX3047]  
uPD78F0511AGA@TQFP48 [CX3047]  
uPD78F0511AGB(A2)@TQFP44 [CX3005]  
uPD78F0511AGB@TQFP44 [CX3005]  
uPD78F0511GA(A)@TQFP48 [CX3047]  
uPD78F0511GA@TQFP48 [CX3047]  
uPD78F0511GB(A2)@TQFP44 [CX3005]  
uPD78F0511MC@SSOP38 [CX1027]  
uPD78F0512AGA(A2)@TQFP48 [CX3047]  
uPD78F0512AGA@TQFP48 [CX3047]  
uPD78F0512AGB(A2)@TQFP44 [CX3005]  
uPD78F0512AGB@TQFP44 [CX3005]  
uPD78F0512GA(A)@TQFP48 [CX3047]  
uPD78F0512GA@TQFP48 [CX3047]  
uPD78F0512GB(A2)@TQFP44 [CX3005]  
uPD78F0512MC@SSOP38 [CX1027]  
uPD78F0513ADGA(A)@TQFP48 [CX3047]  
uPD78F0513ADGA(A2)@TQFP48 [CX3047]  
uPD78F0513ADGA@TQFP48 [CX3047]  
uPD78F0513ADGB(A)@TQFP44 [CX3005]  
uPD78F0513ADGB(A2)@TQFP44 [CX3005]  
uPD78F0513ADGB@TQFP44 [CX3005]  
uPD78F0513AGA(A)@TQFP48 [CX3047]  
uPD78F0513AGA(A2)@TQFP48 [CX3047]  
uPD78F0513AGA@TQFP48 [CX3047]  
uPD78F0513AGB(A2)@TQFP44 [CX3005]  
uPD78F0513AGB@TQFP44 [CX3005]  
uPD78F0513DGA(A)@TQFP48 [CX3047]  
uPD78F0513DGA(A2)@TQFP48 [CX3047]  
uPD78F0513DGA@TQFP48 [CX3047]  
uPD78F0513DGB(A2)@TQFP44 [CX3005]  
uPD78F0513DGB@TQFP44 [CX3005]  
uPD78F0513GA(A)@TQFP48 [CX3047]  
uPD78F0513GA@TQFP48 [CX3047]  
uPD78F0513GB(A2)@TQFP44 [CX3005]  
uPD78F0513MC@SSOP38 [CX1027]  
uPD78F0514AGA(A2)@TQFP48 [CX3047]  
uPD78F0514AGA@TQFP48 [CX3047]  
uPD78F0514AGB(A2)@TQFP44 [CX3005]  
uPD78F0514AGB@TQFP44 [CX3005]  
uPD78F0514GA(A)@TQFP48 [CX3047]  
uPD78F0514GA@TQFP48 [CX3047]  
uPD78F0514GB(A2)@TQFP44 [CX3005]  
uPD78F0501MC(A)@SSOP30 [CX1027]  
uPD78F0502AAQS [CX1027]  
uPD78F0502AFC@FLGA36  
uPD78F0502AMC@SSOP30 [CX1027]  
uPD78F0502AQSA [CX1027]  
uPD78F0502MC(A)@SSOP30 [CX1027]  
uPD78F0503AAQS [CX1027]  
uPD78F0503ADFC@FLGA36  
uPD78F0503AFC@FLGA36  
uPD78F0503AMC@SSOP30 [CX1027]  
uPD78F0503AQSA [CX1027]  
uPD78F0503DMC(A)@SSOP30 [CX1027]  
uPD78F0503FC@FLGA36  
uPD78F0503MC@SSOP30 [CX1027]  
uPD78F0511AGB(A)@TQFP44 [CX3005]  
uPD78F0511AMC@SSOP38 [CX1027]  
uPD78F0511GA(A2)@TQFP48 [CX3047]  
uPD78F0511GB(A)@TQFP44 [CX3005]  
uPD78F0511GB@TQFP44 [CX3005]  
uPD78F0512AGA(A)@TQFP48 [CX3047]  
uPD78F0512AGB(A)@TQFP44 [CX3005]  
uPD78F0512AMC@SSOP38 [CX1027]  
uPD78F0512GA(A2)@TQFP48 [CX3047]  
uPD78F0512GB(A)@TQFP44 [CX3005]  
uPD78F0512GB@TQFP44 [CX3005]  
uPD78F0513ADMC@SSOP38 [CX1027]  
uPD78F0513AGB(A)@TQFP44 [CX3005]  
uPD78F0513AMC@SSOP38 [CX1027]  
uPD78F0513DGB(A)@TQFP44 [CX3005]  
uPD78F0513DMC@SSOP38 [CX1027]  
uPD78F0513GA(A2)@TQFP48 [CX3047]  
uPD78F0513GB(A)@TQFP44 [CX3005]  
uPD78F0513GB@TQFP44 [CX3005]  
uPD78F0514AGA(A)@TQFP48 [CX3047]  
uPD78F0514AGB(A)@TQFP44 [CX3005]  
uPD78F0514AMC@SSOP38 [CX1027]  
uPD78F0514GA(A2)@TQFP48 [CX3047]  
uPD78F0514GB(A)@TQFP44 [CX3005]  
uPD78F0514GB@TQFP44 [CX3005]



uPD78F0514MC@SSOP38 [CX1027] uPD78F0515AGA(A)@TQFP48 [CX3047]  
uPD78F0515AGA(A2)@TQFP48 [CX3047] uPD78F0515AGB(A)@TQFP44 [CX3005]  
uPD78F0515AGA@TQFP48 [CX3047] uPD78F0515AGB(A2)@TQFP44 [CX3005]  
uPD78F0515AGB(A2)@TQFP44 [CX3005] uPD78F0515AMC@SSOP38 [CX1027]  
uPD78F0515GA(A)@TQFP48 [CX3047] uPD78F0515GA(A2)@TQFP48 [CX3047]  
uPD78F0515GA@TQFP48 [CX3047] uPD78F0515GB(A)@TQFP44 [CX3005]  
uPD78F0515GB(A2)@TQFP44 [CX3005] uPD78F0515GB@TQFP44 [CX3005]  
uPD78F0515MC@SSOP38 [CX1027] uPD78F0521AGB(A)@LQFP52 [CX3010]  
uPD78F0521AGB(A2)@LQFP52 [CX3010] uPD78F0521AGB(A)@LQFP52 [CX3010]  
uPD78F0521AGB@LQFP52 [CX3010] uPD78F0521GB(A)@LQFP52(Uart) [CX3010]  
uPD78F0521GB(A2)@LQFP52 [CX3010] uPD78F0521GB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0521GB@LQFP52 [CX3010] uPD78F0521GB@LQFP52(Uart) [CX3010]  
uPD78F0522AGB(A)@LQFP52 [CX3010] uPD78F0522AGB(A2)@LQFP52 [CX3010]  
uPD78F0522AGB@LQFP52 [CX3010] uPD78F0522GB(A)@LQFP52 [CX3010]  
uPD78F0522GB(A)@LQFP52(Uart) [CX3010] uPD78F0522GB(A2)@LQFP52 [CX3010]  
uPD78F0522GB(A2)@LQFP52 [CX3010] uPD78F0522GB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0522GB@LQFP52 [CX3010] uPD78F0522GB@LQFP52(Uart) [CX3010]  
uPD78F0523ADGB(A)@LQFP52 [CX3010] uPD78F0523ADGB(A2)@LQFP52 [CX3010]  
uPD78F0523ADGB@LQFP52 [CX3010] uPD78F0523AGB(A)@LQFP52 [CX3010]  
uPD78F0523AGB(A2)@LQFP52 [CX3010] uPD78F0523AGB@LQFP52 [CX3010]  
uPD78F0523DGB(A)@LQFP52 [CX3010] uPD78F0523DGB(A)@LQFP52 [CX3010]  
uPD78F0523DGB(A)@LQFP52(Uart) [CX3010] uPD78F0523DGB(A2)@LQFP52 [CX3010]  
uPD78F0523DGB(A2)@LQFP52 [CX3010] uPD78F0523DGB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0523DGB@LQFP52 [CX3010] uPD78F0523DGB@LQFP52(Uart) [CX3010]  
uPD78F0523GB(A)@LQFP52 [CX3010] uPD78F0523GB(A)@LQFP52(Uart) [CX3010]  
uPD78F0523GB(A2)@LQFP52 [CX3010] uPD78F0523GB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0523GB@LQFP52 [CX3010] uPD78F0523GB@LQFP52(Uart) [CX3010]  
uPD78F0524AGB(A)@LQFP52 [CX3010] uPD78F0524AGB(A2)@LQFP52 [CX3010]  
uPD78F0524AGB@LQFP52 [CX3010] uPD78F0524GB(A)@LQFP52 [CX3010]  
uPD78F0524GB(A)@LQFP52(Uart) [CX3010] uPD78F0524GB(A2)@LQFP52 [CX3010]  
uPD78F0524GB(A2)@LQFP52 [CX3010] uPD78F0524GB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0524GB@LQFP52 [CX3010] uPD78F0524GB@LQFP52(Uart) [CX3010]  
uPD78F0525AGB(A)@LQFP52 [CX3010] uPD78F0525AGB(A2)@LQFP52 [CX3010]  
uPD78F0525AGB@LQFP52 [CX3010] uPD78F0525GB(A)@LQFP52 [CX3010]  
uPD78F0525GB(A)@LQFP52(Uart) [CX3010] uPD78F0525GB(A2)@LQFP52 [CX3010]  
uPD78F0525GB(A2)@LQFP52 [CX3010] uPD78F0525GB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0525GB@LQFP52 [CX3010] uPD78F0525GB@LQFP52(Uart) [CX3010]  
uPD78F0526AGB(A)@LQFP52 [CX3010] uPD78F0526AGB(A2)@LQFP52 [CX3010]  
uPD78F0526AGB@LQFP52 [CX3010] uPD78F0526GB(A)@LQFP52 [CX3010]

uPD78F0526GB(A)@LQFP52(Uart) [CX3010]  
uPD78F0526GB(A2)@LQFP52 [CX3010]  
uPD78F0526GB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0526GB@LQFP52 [CX3010]  
uPD78F0526GB@LQFP52(Uart) [CX3010]  
uPD78F0527AGB(A)@LQFP52 [CX3010]  
uPD78F0527AGB(A2)@LQFP52 [CX3010]  
uPD78F0527AGB@LQFP52 [CX3010] uPD78F0527GB(A)@LQFP52 [CX3010]  
uPD78F0527GB(A)@LQFP52(Uart) [CX3010]  
uPD78F0527GB(A2)@LQFP52 [CX3010]  
uPD78F0527GB(A2)@LQFP52(Uart) [CX3010]  
uPD78F0527GB@LQFP52 [CX3010]  
uPD78F0527GB@LQFP52(Uart) [CX3010]  
uPD78F0531AGB(A)@LQFP64 [CX3011]  
uPD78F0531AGB(A2)@LQFP64 [CX3011]  
uPD78F0531AGB@LQFP64 [CX3011] uPD78F0531AGC(A)@LQFP64 [CX3013]  
uPD78F0531AGC(A2)@LQFP64 [CX3013]  
uPD78F0531AGC@LQFP64 [CX3013] uPD78F0531AGK(A)@LQFP64 [CX3012]  
uPD78F0531AGK(A2)@LQFP64 [CX3012]  
uPD78F0531AGK@LQFP64 [CX3012] uPD78F0531GB(A)@LQFP64 [CX3011]  
uPD78F0531GB(A2)@LQFP64 [CX3011] uPD78F0531GB@LQFP64 [CX3011]  
uPD78F0531GC(A)@LQFP64 [CX3013] uPD78F0531GC(A2)@LQFP64 [CX3013]  
uPD78F0531GC@LQFP64 [CX3013] uPD78F0531GK(A)@LQFP64 [CX3012]  
uPD78F0531GK(A2)@LQFP64 [CX3012] uPD78F0531GK@LQFP64 [CX3012]  
uPD78F0532AGB(A)@LQFP64 [CX3011]  
uPD78F0532AGB(A2)@LQFP64 [CX3011] uPD78F0532AGC(A)@LQFP64 [CX3013]  
uPD78F0532AGB@LQFP64 [CX3011] uPD78F0532AGC(A2)@LQFP64 [CX3013]  
uPD78F0532AGC(A2)@LQFP64 [CX3013] uPD78F0532AGK(A)@LQFP64 [CX3012]  
uPD78F0532AGC@LQFP64 [CX3013] uPD78F0532AGK(A2)@LQFP64 [CX3012]  
uPD78F0532AGK(A2)@LQFP64 [CX3012] uPD78F0532AGK@LQFP64 [CX3012]  
uPD78F0532AGK@LQFP64 [CX3012] uPD78F0532GB(A)@LQFP64 [CX3011]  
uPD78F0532GB(A2)@LQFP64 [CX3011] uPD78F0532GB@LQFP64 [CX3011]  
uPD78F0532GC(A)@LQFP64 [CX3013] uPD78F0532GC(A2)@LQFP64 [CX3013]  
uPD78F0532GC@LQFP64 [CX3013] uPD78F0532GK(A)@LQFP64 [CX3012]  
uPD78F0532GK(A2)@LQFP64 [CX3012] uPD78F0532GK@LQFP64 [CX3012]  
uPD78F0533ADGB(A)@LQFP64 [CX3011]  
uPD78F0533ADGB(A2)@LQFP64 [CX3011] uPD78F0533ADGB@LQFP64 [CX3011]  
uPD78F0533ADGB@LQFP64 [CX3011] uPD78F0533ADGC(A)@LQFP64 [CX3013]  
uPD78F0533ADGC(A2)@LQFP64 [CX3013] uPD78F0533ADGC@LQFP64 [CX3013]  
uPD78F0533ADGC@LQFP64 [CX3013] uPD78F0533ADGK(A)@LQFP64 [CX3012]  
uPD78F0533ADGK(A2)@LQFP64 [CX3012] uPD78F0533ADGK@LQFP64 [CX3012]  
uPD78F0533ADGK@LQFP64 [CX3012] uPD78F0533AGB(A)@LQFP64 [CX3011]  
uPD78F0533AGB(A2)@LQFP64 [CX3011] uPD78F0533AGB@LQFP64 [CX3011]  
uPD78F0533AGB@LQFP64 [CX3011] uPD78F0533AGC(A)@LQFP64 [CX3013]  
uPD78F0533AGC(A2)@LQFP64 [CX3013] uPD78F0533AGC@LQFP64 [CX3013]  
uPD78F0533AGC@LQFP64 [CX3013] uPD78F0533AGK(A)@LQFP64 [CX3012]  
uPD78F0533AGK(A2)@LQFP64 [CX3012] uPD78F0533AGK@LQFP64 [CX3012]  
uPD78F0533AGK@LQFP64 [CX3012] uPD78F0533DGB(A)@LQFP64 [CX3011]  
uPD78F0533DGB(A2)@LQFP64 [CX3011] uPD78F0533DGB@LQFP64 [CX3011]  
uPD78F0533DGB@LQFP64 [CX3011] uPD78F0533DGC(A)@LQFP64 [CX3013]  
uPD78F0533DGC(A2)@LQFP64 [CX3013] uPD78F0533DGC@LQFP64 [CX3013]  
uPD78F0533DGC@LQFP64 [CX3013] uPD78F0533DGK(A)@LQFP64 [CX3012]  
uPD78F0533DGC@LQFP64 [CX3013] uPD78F0533DGK@LQFP64 [CX3012]  
uPD78F0533DGK(A2)@LQFP64 [CX3012] uPD78F0533DGK@LQFP64 [CX3012]  
uPD78F0533DGK@LQFP64 [CX3012] uPD78F0533GB(A)@LQFP64 [CX3011]  
uPD78F0533GB(A2)@LQFP64 [CX3011] uPD78F0533GB@LQFP64 [CX3011]  
uPD78F0533GB@LQFP64 [CX3011] uPD78F0533GC(A)@LQFP64 [CX3013]  
uPD78F0533GC(A2)@LQFP64 [CX3013] uPD78F0533GC@LQFP64 [CX3013]  
uPD78F0533GC@LQFP64 [CX3013] uPD78F0533GK(A)@LQFP64 [CX3012]

uPD78F0533GK(A2)@LQFP64 [CX3012]  
uPD78F0534AGB(A)@LQFP64 [CX3011]  
uPD78F0534AGB(A2)@LQFP64 [CX3011]  
uPD78F0534AGB@LQFP64 [CX3011]  
uPD78F0534AGC(A2)@LQFP64 [CX3013]  
uPD78F0534AGC@LQFP64 [CX3013]  
uPD78F0534AGK(A2)@LQFP64 [CX3012]  
uPD78F0534AGK@LQFP64 [CX3012]  
uPD78F0534GB(A2)@LQFP64 [CX3011]  
uPD78F0534GC(A)@LQFP64 [CX3013]  
uPD78F0534GC@LQFP64 [CX3013]  
uPD78F0534GK(A2)@LQFP64 [CX3012]  
uPD78F0535AGB(A)@LQFP64 [CX3011]  
uPD78F0535AGB(A2)@LQFP64 [CX3011]  
uPD78F0535AGB@LQFP64 [CX3011]  
uPD78F0535AGC(A2)@LQFP64 [CX3013]  
uPD78F0535AGC@LQFP64 [CX3013]  
uPD78F0535AGK(A2)@LQFP64 [CX3012]  
uPD78F0535AGK@LQFP64 [CX3012]  
uPD78F0535GB(A2)@LQFP64 [CX3011]  
uPD78F0535GC(A)@LQFP64 [CX3013]  
uPD78F0535GC@LQFP64 [CX3013]  
uPD78F0535GK(A2)@LQFP64 [CX3012]  
uPD78F0536AGB(A)@LQFP64 [CX3011]  
uPD78F0536AGB(A2)@LQFP64 [CX3011]  
uPD78F0536AGB@LQFP64 [CX3011]  
uPD78F0536AGC(A2)@LQFP64 [CX3013]  
uPD78F0536AGC@LQFP64 [CX3013]  
uPD78F0536AGK(A2)@LQFP64 [CX3012]  
uPD78F0536AGK@LQFP64 [CX3012]  
uPD78F0536GB(A2)@LQFP64 [CX3011]  
uPD78F0536GC(A)@LQFP64 [CX3013]  
uPD78F0536GC@LQFP64 [CX3013]  
uPD78F0536GK(A2)@LQFP64 [CX3012]  
uPD78F0537ADGB(A)@LQFP64 [CX3011]  
uPD78F0537ADGB(A2)@LQFP64 [CX3011]  
uPD78F0537ADGB@LQFP64 [CX3011]  
uPD78F0537ADGC(A)@LQFP64 [CX3013]  
uPD78F0537ADGC(A2)@LQFP64 [CX3013]  
uPD78F0537ADGC@LQFP64 [CX3013]  
uPD78F0537ADGK(A)@LQFP64 [CX3012]  
uPD78F0537ADGK(A2)@LQFP64 [CX3012]  
uPD78F0537ADGK@LQFP64 [CX3012]  
uPD78F0537AGB(A2)@LQFP64 [CX3011]  
uPD78F0537AGB@LQFP64 [CX3011]  
uPD78F0537AGC(A2)@LQFP64 [CX3013]  
uPD78F0537AGC@LQFP64 [CX3013]  
uPD78F0537AGK(A2)@LQFP64 [CX3012]  
uPD78F0537AGK@LQFP64 [CX3012]  
uPD78F0537DGB(A2)@LQFP64 [CX3011]  
uPD78F0537DGB@LQFP64 [CX3011]  
uPD78F0537DGC(A2)@LQFP64 [CX3013]  
uPD78F0537DGC@LQFP64 [CX3013]  
uPD78F0537DGK(A2)@LQFP64 [CX3012]  
uPD78F0537DGK@LQFP64 [CX3012]  
uPD78F0537GB(A2)@LQFP64 [CX3011]  
uPD78F0537GC(A)@LQFP64 [CX3013]  
uPD78F0537GC@LQFP64 [CX3013]  
uPD78F0537GK(A2)@LQFP64 [CX3012]

uPD78F0533GK@LQFP64 [CX3012]  
  
uPD78F0534AGC(A)@LQFP64 [CX3013]  
uPD78F0534AGK(A)@LQFP64 [CX3012]  
uPD78F0534GB(A)@LQFP64 [CX3011]  
uPD78F0534GB@LQFP64 [CX3011]  
uPD78F0534GC(A2)@LQFP64 [CX3013]  
uPD78F0534GK(A)@LQFP64 [CX3012]  
uPD78F0534GK@LQFP64 [CX3012]  
  
uPD78F0535AGC(A)@LQFP64 [CX3013]  
uPD78F0535AGK(A)@LQFP64 [CX3012]  
uPD78F0535GB(A)@LQFP64 [CX3011]  
uPD78F0535GB@LQFP64 [CX3011]  
uPD78F0535GC(A2)@LQFP64 [CX3013]  
uPD78F0535GK(A)@LQFP64 [CX3012]  
uPD78F0535GK@LQFP64 [CX3012]  
  
uPD78F0536AGC(A)@LQFP64 [CX3013]  
uPD78F0536AGK(A)@LQFP64 [CX3012]  
uPD78F0536GB(A)@LQFP64 [CX3011]  
uPD78F0536GB@LQFP64 [CX3011]  
uPD78F0536GC(A2)@LQFP64 [CX3013]  
uPD78F0536GK(A)@LQFP64 [CX3012]  
uPD78F0536GK@LQFP64 [CX3012]  
  
uPD78F0536AGC(A)@LQFP64 [CX3013]  
uPD78F0536AGK(A)@LQFP64 [CX3012]  
uPD78F0536GB(A)@LQFP64 [CX3011]  
uPD78F0536GB@LQFP64 [CX3011]  
uPD78F0536GC(A2)@LQFP64 [CX3013]  
uPD78F0536GK(A)@LQFP64 [CX3012]  
uPD78F0536GK@LQFP64 [CX3012]  
  
uPD78F0537AGB(A)@LQFP64 [CX3011]  
uPD78F0537AGC(A)@LQFP64 [CX3013]  
uPD78F0537AGK(A)@LQFP64 [CX3012]  
  
uPD78F0537DGB(A)@LQFP64 [CX3011]  
uPD78F0537DGC(A)@LQFP64 [CX3013]  
uPD78F0537DGK(A)@LQFP64 [CX3012]  
  
uPD78F0537GB(A)@LQFP64 [CX3011]  
uPD78F0537GB@LQFP64 [CX3011]  
uPD78F0537GC(A2)@LQFP64 [CX3013]  
uPD78F0537GK(A)@LQFP64 [CX3012]  
uPD78F0537GK@LQFP64 [CX3012]

uPD78F0544AGC(A)@LQFP80 [CX3017]  
uPD78F0544AGC(A2)@LQFP80 [CX3017]  
uPD78F0544AGC@LQFP80 [CX3017]  
uPD78F0544AGK(A2)@LQFP80 [CX3016]  
uPD78F0544AGK@LQFP80 [CX3016]  
uPD78F0544GC(A2)@LQFP80 [CX3017]  
uPD78F0544GK(A)@LQFP80 [CX3016]  
uPD78F0544GK@LQFP80 [CX3016]  
uPD78F0545AGC(A2)@LQFP80 [CX3017]  
uPD78F0545AGC@LQFP80 [CX3017]  
uPD78F0545AGK(A2)@LQFP80 [CX3016]  
uPD78F0545AGK@LQFP80 [CX3016]  
uPD78F0545GC(A2)@LQFP80 [CX3017]  
uPD78F0545GK(A)@LQFP80 [CX3016]  
uPD78F0545GK@LQFP80 [CX3016]  
uPD78F0546AGK(A2)@LQFP80 [CX3016]  
uPD78F0546AGK@LQFP80 [CX3016]  
uPD78F0546GK(A2)@LQFP80 [CX3016]  
uPD78F0547ADGC(A)@LQFP80 [CX3017]  
uPD78F0547ADGC(A2)@LQFP80 [CX3017]  
uPD78F0547ADGC@LQFP80 [CX3017]  
uPD78F0547ADGK(A)@LQFP80 [CX3016]  
uPD78F0547ADGK(A2)@LQFP80 [CX3016]  
uPD78F0547ADGK@LQFP80 [CX3016]  
uPD78F0547AGC(A2)@LQFP80 [CX3017]  
uPD78F0547AGC@LQFP80 [CX3017]  
uPD78F0547AGK(A2)@LQFP80 [CX3016]  
uPD78F0547AGK@LQFP80 [CX3016]  
uPD78F0547DGC(A2)@LQFP80 [CX3017]  
uPD78F0547DGC@LQFP80 [CX3017]  
uPD78F0547DGK(A2)@LQFP80 [CX3016]  
uPD78F0547DGK@LQFP80 [CX3016]  
uPD78F0547GC(A2)@LQFP80 [CX3017]  
uPD78F0547GK(A)@LQFP80 [CX3016]  
uPD78F0547GK@LQFP80 [CX3016]  
uPD78F0550MC@SSOP16 [CX1016]  
uPD78F0551MC@SSOP16 [CX1016]  
uPD78F0552MC@SSOP16 [CX1016]  
uPD78F0553MC@SSOP16 [CX1016]  
uPD78F0555MC@SSOP16 [CX1016]  
uPD78F0556MC@SSOP16 [CX1016]  
uPD78F0557MC@SSOP16 [CX1016]  
uPD78F0558MC@SSOP16 [CX1016]  
uPD78F0560K@WQFN32 [CX4015]  
uPD78F0561FC@FLGA25 [CX0001]  
uPD78F0561MC@SSOP20 [CX1027]  
uPD78F0562K@WQFN32 [CX4015]  
uPD78F0563FC@FLGA25 [CX0001]  
uPD78F0563MC@SSOP20 [CX1027]  
uPD78F0565K@WQFN32 [CX4015]  
uPD78F0566FC@FLGA25 [CX0001]  
uPD78F0566MC@SSOP20 [CX1027]  
uPD78F0567K@WQFN32 [CX4015]  
uPD78F0568FC@FLGA25 [CX0001]  
uPD78F0568MC@SSOP20 [CX1027]  
uPD78F0571MC@SSOP30 [CX1027]  
uPD78F0573MC@SSOP30 [CX1027]  
uPD78F0576MC@SSOP30 [CX1027]  
uPD78F0578MC@SSOP30 [CX1027]  
uPD78F0544AGK(A)@LQFP80 [CX3016]  
uPD78F0544GC(A)@LQFP80 [CX3017]  
uPD78F0544GC@LQFP80 [CX3017]  
uPD78F0544GK(A2)@LQFP80 [CX3016]  
uPD78F0545AGC(A)@LQFP80 [CX3017]  
uPD78F0545AGK(A)@LQFP80 [CX3016]  
uPD78F0545GC(A)@LQFP80 [CX3017]  
uPD78F0545GC@LQFP80 [CX3017]  
uPD78F0545GK(A2)@LQFP80 [CX3016]  
uPD78F0546AGK(A)@LQFP80 [CX3016]  
uPD78F0546GK(A)@LQFP80 [CX3016]  
uPD78F0546GK@LQFP80 [CX3016]  
uPD78F0547AGC(A)@LQFP80 [CX3017]  
uPD78F0547AGK(A)@LQFP80 [CX3016]  
uPD78F0547DGC(A)@LQFP80 [CX3017]  
uPD78F0547DGK(A)@LQFP80 [CX3016]  
uPD78F0547GC(A)@LQFP80 [CX3017]  
uPD78F0547GC@LQFP80 [CX3017]  
uPD78F0547GK(A2)@LQFP80 [CX3016]  
uPD78F0550MA@SSOP16 [CX1016]  
uPD78F0551MA@SSOP16 [CX1016]  
uPD78F0552MA@SSOP16 [CX1016]  
uPD78F0553MA@SSOP16 [CX1016]  
uPD78F0555MA@SSOP16 [CX1016]  
uPD78F0556MA@SSOP16 [CX1016]  
uPD78F0557MA@SSOP16 [CX1016]  
uPD78F0558MA@SSOP16 [CX1016]  
uPD78F0560FC@FLGA25 [CX0001]  
uPD78F0560MC@SSOP20 [CX1027]  
uPD78F0561K@WQFN32 [CX4015]  
uPD78F0562FC@FLGA25 [CX0001]  
uPD78F0562MC@SSOP20 [CX1027]  
uPD78F0563K@WQFN32 [CX4015]  
uPD78F0565FC@FLGA25 [CX0001]  
uPD78F0565MC@SSOP20 [CX1027]  
uPD78F0566K@WQFN32 [CX4015]  
uPD78F0567FC@FLGA25 [CX0001]  
uPD78F0567MC@SSOP20 [CX1027]  
uPD78F0568K@WQFN32 [CX4015]  
uPD78F0570MC@SSOP30 [CX1027]  
uPD78F0572MC@SSOP30 [CX1027]  
uPD78F0575MC@SSOP30 [CX1027]  
uPD78F0577MC@SSOP30 [CX1027]  
uPD78F0580GA@LQFP48 [CX3047]

uPD78F0580GB@LQFP44 [CX3005]  
uPD78F0581GA@LQFP48 [CX3047]  
uPD78F0581K@WQFN40 [CX4017]  
uPD78F0582GB@LQFP44 [CX3005]  
uPD78F0583GA@LQFP48 [CX3047]  
uPD78F0583K@WQFN40 [CX4017]  
uPD78F0585GB@LQFP44 [CX3005]  
uPD78F0586GA@LQFP48 [CX3047]  
uPD78F0586K@WQFN40 [CX4017]  
uPD78F0587GB@LQFP44 [CX3005]  
uPD78F0588GA@LQFP48 [CX3047]  
uPD78F0588K@WQFN40 [CX4017]  
uPD78F0591 [CX1027]  
uPD78F0593 [CX3047]  
uPD78F0760 [CX3047]  
uPD78F0762 [CX3047]  
uPD78F0764 [CX3011]  
uPD78F0820B(A)@LQFP100 [CX3043]  
uPD78F0820B(A2)@LQFP100 [CX3043]  
uPD78F0822B(A)@LQFP100 [CX3043]  
uPD78F0822B(A2)@LQFP100 [CX3043]  
uPD78F0824AGC(A)@QFP80 [CX3018]  
uPD78F0824AGC(A2)@QFP80 [CX3018]  
uPD78F0824BGC(A)@QFP80 [CX3018]  
uPD78F0824BGC(A2)@QFP80 [CX3018]  
uPD78F0826AGC(A)@QFP80 [CX3018]  
uPD78F0826AGC(A2)@QFP80 [CX3018]  
uPD78F0826BGC(A)@QFP80 [CX3018]  
uPD78F0826BGC(A2)@QFP80 [CX3018]  
uPD78F0828AGC(A)@QFP80 [CX3018]  
uPD78F0828AGC(A2)@QFP80 [CX3018]  
uPD78F0828BGC(A)@QFP80 [CX3018]  
uPD78F0828BGC(A2)@QFP80 [CX3018]  
uPD78F0836GB(A)@LQFP64 [CX3011]  
uPD78F0836GB@LQFP64 [CX3011]  
uPD78F0837GB(A2)@LQFP64 [CX3011]  
uPD78F0838GK(A)@LQFP80 [CX3016]  
uPD78F0838GK@LQFP80 [CX3016]  
uPD78F0839GK(A2)@LQFP80 [CX3016]  
uPD78F0840GK(A)@LQFP80 [CX3016]  
uPD78F0840GK@LQFP80 [CX3016]  
uPD78F0841GK(A2)@LQFP80 [CX3016]  
uPD78F0842GK(A)@LQFP80 [CX3016]  
uPD78F0842GK@LQFP80 [CX3016]  
uPD78F0843GK(A2)@LQFP80 [CX3016]  
uPD78F0844GB(A)@LQFP64 [CX3011]  
uPD78F0844GB@LQFP64 [CX3011]  
uPD78F0845GB(A2)@LQFP64 [CX3011]  
uPD78F0846GK(A)@LQFP80 [CX3016]  
uPD78F0846GK@LQFP80 [CX3016]  
uPD78F0847GK(A2)@LQFP80 [CX3016]  
uPD78F0848GK(A)@LQFP80 [CX3016]  
uPD78F0848GK@LQFP80 [CX3016]  
uPD78F0849GK(A2)@LQFP80 [CX3016]  
uPD78F0854MA [CX1001]  
uPD78F0856MA [CX1001]  
uPD78F0858MC [CX1027]  
uPD78F0864MC [CX1027]  
uPD78F1142AGA [CX3064]

uPD78F0580K@WQFN40 [CX4017]  
uPD78F0581GB@LQFP44 [CX3005]  
uPD78F0582GA@LQFP48 [CX3047]  
uPD78F0582K@WQFN40 [CX4017]  
uPD78F0583GB@LQFP44 [CX3005]  
uPD78F0585GA@LQFP48 [CX3047]  
uPD78F0585K@WQFN40 [CX4017]  
uPD78F0586GB@LQFP44 [CX3005]  
uPD78F0587GA@LQFP48 [CX3047]  
uPD78F0587K@WQFN40 [CX4017]  
uPD78F0588GB@LQFP44 [CX3005]  
uPD78F0590 [CX1027]  
uPD78F0592 [CX3047]  
uPD78F0730 [CX1027]  
uPD78F0761 [CX3047]  
uPD78F0763 [CX3011]  
uPD78F0765 [CX3011]  
uPD78F0820B(A1)@LQFP100 [CX3043]  
uPD78F0820B@LQFP100 [CX3043]  
uPD78F0822B(A1)@LQFP100 [CX3043]  
uPD78F0822B@LQFP100 [CX3043]  
uPD78F0824AGC(A1)@QFP80 [CX3018]  
uPD78F0824AGC@QFP80 [CX3018]  
uPD78F0824BGC(A1)@QFP80 [CX3018]  
uPD78F0824BGC@QFP80 [CX3018]  
uPD78F0826AGC(A1)@QFP80 [CX3018]  
uPD78F0826AGC@QFP80 [CX3018]  
uPD78F0826BGC(A1)@QFP80 [CX3018]  
uPD78F0826BGC@QFP80 [CX3018]  
uPD78F0828AGC(A1)@QFP80 [CX3018]  
uPD78F0828AGC@QFP80 [CX3018]  
uPD78F0828BGC(A1)@QFP80 [CX3018]  
uPD78F0828BGC@QFP80 [CX3018]  
uPD78F0836GB(A2)@LQFP64 [CX3011]  
uPD78F0837GB(A)@LQFP64 [CX3011]  
uPD78F0837GB@LQFP64 [CX3011]  
uPD78F0838GK(A2)@LQFP80 [CX3016]  
uPD78F0839GK(A)@LQFP80 [CX3016]  
uPD78F0839GK@LQFP80 [CX3016]  
uPD78F0840GK(A2)@LQFP80 [CX3016]  
uPD78F0841GK(A)@LQFP80 [CX3016]  
uPD78F0841GK@LQFP80 [CX3016]  
uPD78F0842GK(A2)@LQFP80 [CX3016]  
uPD78F0843GK(A)@LQFP80 [CX3016]  
uPD78F0843GK@LQFP80 [CX3016]  
uPD78F0844GB(A2)@LQFP64 [CX3011]  
uPD78F0845GB(A)@LQFP64 [CX3011]  
uPD78F0845GB@LQFP64 [CX3011]  
uPD78F0846GK(A2)@LQFP80 [CX3016]  
uPD78F0847GK(A)@LQFP80 [CX3016]  
uPD78F0847GK@LQFP80 [CX3016]  
uPD78F0848GK(A2)@LQFP80 [CX3016]  
uPD78F0849GK(A)@LQFP80 [CX3016]  
uPD78F0849GK@LQFP80 [CX3016]  
uPD78F0855MA [CX1001]  
uPD78F0857MC [CX1027]  
uPD78F0859MC [CX1027]  
uPD78F0865MC [CX1027]  
uPD78F1142AGB [CX3011]

uPD78F1142AGK [CX3012]  
uPD78F1142GB@LQFP64 [CX3011]  
uPD78F1143AGA [CX3064]  
uPD78F1143AGK [CX3012]  
uPD78F1143GB@LQFP64 [CX3011]  
uPD78F1144AGA [CX3064]  
uPD78F1144AGK [CX3012]  
uPD78F1144GB@LQFP64 [CX3011]  
uPD78F1145AGA [CX3064]  
uPD78F1145AGK [CX3012]  
uPD78F1145GB@LQFP64 [CX3011]  
uPD78F1146AGA [CX3064]  
uPD78F1146AGK [CX3012]  
uPD78F1146GB@LQFP64 [CX3011]  
uPD78F1152AGC [CX3018]  
uPD78F1152GC@LQFP80 [CX3018]  
uPD78F1153AGC [CX3018]  
uPD78F1153GC@LQFP80 [CX3018]  
uPD78F1154AGC [CX3018]  
uPD78F1154GC@LQFP80 [CX3018]  
uPD78F1155AGC [CX3018]  
uPD78F1155GC@LQFP80 [CX3018]  
uPD78F1156AGC [CX3018]  
uPD78F1156GC@LQFP80 [CX3018]  
uPD78F1162@LQFP100 [CX3062]  
uPD78F1162AGC [CX3043]  
uPD78F1162GC@LQFP100 [CX3043]  
uPD78F1163@LQFP100 [CX3062]  
uPD78F1163AGC [CX3043]  
uPD78F1163GC@LQFP100 [CX3043]  
uPD78F1164@LQFP100 [CX3062]  
uPD78F1164AGC [CX3023]  
uPD78F1164GC@LQFP100 [CX3023]  
uPD78F1165@LQFP100 [CX3062]  
uPD78F1165AGC [CX3043]  
uPD78F1165GC@LQFP100 [CX3043]  
uPD78F1166@LQFP100 [CX3062]  
uPD78F1166AGC [CX3043]  
uPD78F1166GC@LQFP100 [CX3043]  
uPD78F1167@LQFP100 [CX3062]  
uPD78F1167AGC [CX3043]  
uPD78F1167GC@LQFP100 [CX3043]  
uPD78F1168@LQFP100 [CX3062]  
uPD78F1168AGC [CX3043]  
uPD78F1168GC@LQFP100 [CX3043]  
uPD78F1201MC@SSOP30 [CX1027]  
uPD78F1204MC@SSOP30 [CX1027]  
uPD78F1211GA@QFP48 [CX3007]  
uPD78F1211MC@SSOP38 [CX1027]  
uPD78F1213GB@QFP44 [CX3002]  
uPD78F1214GA@QFP48 [CX3007]  
uPD78F1214MC@SSOP38 [CX1027]  
uPD78F1215GB@QFP44 [CX3002]  
uPD78F1221GB@QFP52 [CX3009]  
uPD78F1224GB@QFP52 [CX3009]  
uPD78F1231GB@QFP64 [CX3011]  
uPD78F1233GB@QFP64 [CX3011]  
uPD78F1234GB@QFP64 [CX3011]  
uPD78F1235GB@QFP64 [CX3011]

uPD78F1142GA@TQFP64 [CX3064]  
uPD78F1142GK@LQFP64 [CX3012]  
uPD78F1143AGB [CX3011]  
uPD78F1143GA@TQFP64 [CX3064]  
uPD78F1143GK@LQFP64 [CX3012]  
uPD78F1144AGB [CX3011]  
uPD78F1144GA@TQFP64 [CX3064]  
uPD78F1144GK@LQFP64 [CX3012]  
uPD78F1145AGB [CX3011]  
uPD78F1145GA@TQFP64 [CX3064]  
uPD78F1145GK@LQFP64 [CX3012]  
uPD78F1146AGB [CX3011]  
uPD78F1146GA@TQFP64 [CX3064]  
uPD78F1146GK@LQFP64 [CX3012]  
uPD78F1152AGK [CX3016]  
uPD78F1152GK@LQFP80 [CX3016]  
uPD78F1153AGK [CX3016]  
uPD78F1153GK@LQFP80 [CX3016]  
uPD78F1154AGK [CX3016]  
uPD78F1154GK@LQFP80 [CX3016]  
uPD78F1155AGK [CX3016]  
uPD78F1155GK@LQFP80 [CX3016]  
uPD78F1156AGK [CX3016]  
uPD78F1156GK@LQFP80 [CX3016]  
uPD78F1162A [CX3062]  
uPD78F1162AGF [CX3062]  
uPD78F1162GF@LQFP100 [CX3062]  
uPD78F1163A [CX3062]  
uPD78F1163AGF [CX3062]  
uPD78F1163GF@LQFP100 [CX3062]  
uPD78F1164A [CX3062]  
uPD78F1164AGF [CX3062]  
uPD78F1164GF@LQFP100 [CX3062]  
uPD78F1165A [CX3062]  
uPD78F1165AGF [CX3062]  
uPD78F1165GF@LQFP100 [CX3062]  
uPD78F1166A [CX3062]  
uPD78F1166AGF [CX3062]  
uPD78F1166GF@LQFP100 [CX3062]  
uPD78F1167A [CX3062]  
uPD78F1167AGF [CX3062]  
uPD78F1167GF@LQFP100 [CX3062]  
uPD78F1168A [CX3062]  
uPD78F1168AGF [CX3062]  
uPD78F1168GF@LQFP100 [CX3062]  
uPD78F1203MC@SSOP30 [CX1027]  
uPD78F1205MC@SSOP30 [CX1027]  
uPD78F1211GB@QFP44 [CX3002]  
uPD78F1213GA@QFP48 [CX3007]  
uPD78F1213MC@SSOP38 [CX1027]  
uPD78F1214GB@QFP44 [CX3002]  
uPD78F1215GA@QFP48 [CX3007]  
uPD78F1215MC@SSOP38 [CX1027]  
uPD78F1223GB@QFP52 [CX3009]  
uPD78F1225GB@QFP52 [CX3009]  
uPD78F1231GK@QFP64 [CX3064]  
uPD78F1233GK@QFP64 [CX3064]  
uPD78F1234GK@QFP64 [CX3064]  
uPD78F1235GK@QFP64 [CX3064]

uPD78F1804AK8 [CX4015]  
uPD78F1804AK8A2 [CX4015]  
uPD78F1804AMCA [CX1027]  
uPD78F1804K8 [CX4015]  
uPD78F1804K8A2 [CX4015]  
uPD78F1804MCA [CX1027]  
uPD78F1805AK8 [CX4015]  
uPD78F1805AK8A2 [CX4015]  
uPD78F1805AMCA [CX1027]  
uPD78F1805K8 [CX4015]  
uPD78F1805K8A2 [CX4015]  
uPD78F1805MCA [CX1027]  
uPD78F1806AK8 [CX4015]  
uPD78F1806AK8A2 [CX4015]  
uPD78F1806AMCA [CX1027]  
uPD78F1806K8 [CX4015]  
uPD78F1806K8A2 [CX4015]  
uPD78F1806MCA [CX1027]  
uPD78F1807AK8 [CX4015]  
uPD78F1807AK8A2 [CX4015]  
uPD78F1807AMCA [CX1027]  
uPD78F1807K8 [CX4015]  
uPD78F1807K8A2 [CX4015]  
uPD78F1807MCA [CX1027]  
uPD78F1808AK8 [CX4017]  
uPD78F1808AK8A2 [CX4017]  
uPD78F1808K8A [CX4017]  
uPD78F1809AK8 [CX4017]  
uPD78F1809AK8A2 [CX4017]  
uPD78F1809K8A [CX4017]  
uPD78F1810AK8 [CX4017]  
uPD78F1810AK8A2 [CX4017]  
uPD78F1810K8A [CX4017]  
uPD78F1811AK8 [CX4017]  
uPD78F1811AK8A2 [CX4017]  
uPD78F1811K8A [CX4017]  
uPD78F1812AGA [CX3007]  
uPD78F1812AGAA2 [CX3007]  
uPD78F1812AK8A [CX3007]  
uPD78F1812GA [CX3007]  
uPD78F1812GAA2 [CX3007]  
uPD78F1812K8A [CX3007]  
uPD78F1813AGA [CX3007]  
uPD78F1813AGAA2 [CX3007]  
uPD78F1813AK8A [CX3007]  
uPD78F1813GA [CX3007]  
uPD78F1813GAA2 [CX3007]  
uPD78F1813K8A [CX3007]  
uPD78F1814AGA [CX3007]  
uPD78F1814AGAA2 [CX3007]  
uPD78F1814AK8A [CX3007]  
uPD78F1814GA [CX3007]  
uPD78F1814GAA2 [CX3007]  
uPD78F1814K8A [CX3007]  
uPD78F1815AGA [CX3007]  
uPD78F1815AGAA2 [CX3007]  
uPD78F1815AK8A [CX3007]  
uPD78F1815GA [CX3007]  
uPD78F1815GAA2 [CX3007]

uPD78F1804AK8A [CX4015]  
uPD78F1804AMC [CX1027]  
uPD78F1804AMCA2 [CX1027]  
uPD78F1804K8A [CX4015]  
uPD78F1804MC [CX1027]  
uPD78F1804MCA2 [CX1027]  
uPD78F1805AK8A [CX4015]  
uPD78F1805AMC [CX1027]  
uPD78F1805AMCA2 [CX1027]  
uPD78F1805K8A [CX4015]  
uPD78F1805MC [CX1027]  
uPD78F1805MCA2 [CX1027]  
uPD78F1806AK8A [CX4015]  
uPD78F1806AMC [CX1027]  
uPD78F1806AMCA2 [CX1027]  
uPD78F1806K8A [CX4015]  
uPD78F1806MC [CX1027]  
uPD78F1806MCA2 [CX1027]  
uPD78F1807AK8A [CX4015]  
uPD78F1807AMC [CX1027]  
uPD78F1807AMCA2 [CX1027]  
uPD78F1807K8A [CX4015]  
uPD78F1807MC [CX1027]  
uPD78F1807MCA2 [CX1027]  
uPD78F1808AK8A [CX4017]  
uPD78F1808K8 [CX4017]  
uPD78F1808K8A2 [CX4017]  
uPD78F1809AK8A [CX4017]  
uPD78F1809K8 [CX4017]  
uPD78F1809K8A2 [CX4017]  
uPD78F1810AK8A [CX4017]  
uPD78F1810K8 [CX4017]  
uPD78F1810K8A2 [CX4017]  
uPD78F1811AK8A [CX4017]  
uPD78F1811K8 [CX4017]  
uPD78F1811K8A2 [CX4017]  
uPD78F1812AGAA [CX3007]  
uPD78F1812AK8 [CX3007]  
uPD78F1812AK8A2 [CX3007]  
uPD78F1812GAA [CX3007]  
uPD78F1812K8 [CX3007]  
uPD78F1812K8A2 [CX3007]  
uPD78F1813AGAA [CX3007]  
uPD78F1813AK8 [CX3007]  
uPD78F1813AK8A2 [CX3007]  
uPD78F1813GAA [CX3007]  
uPD78F1813K8 [CX3007]  
uPD78F1813K8A2 [CX3007]  
uPD78F1814AGAA [CX3007]  
uPD78F1814AK8 [CX3007]  
uPD78F1814AK8A2 [CX3007]  
uPD78F1814GAA [CX3007]  
uPD78F1814K8 [CX3007]  
uPD78F1814K8A2 [CX3007]  
uPD78F1815AGAA [CX3007]  
uPD78F1815AK8 [CX3007]  
uPD78F1815AK8A2 [CX3007]  
uPD78F1815GAA [CX3007]  
uPD78F1815K8 [CX3007]

uPD78F1815K8A [CX3007]  
uPD78F1816AGA [CX3007]  
uPD78F1816AGAA2 [CX3007]  
uPD78F1816AK8A [CX3007]  
uPD78F1816GA [CX3007]  
uPD78F1816GAA2 [CX3007]  
uPD78F1816K8A [CX3007]  
uPD78F1817AGA [CX3007]  
uPD78F1817AGAA2 [CX3007]  
uPD78F1817AK8A [CX3007]  
uPD78F1817GA [CX3007]  
uPD78F1817GAA2 [CX3007]  
uPD78F1817K8A [CX3007]  
uPD78F1818AGB [CX3011]  
uPD78F1818AGBA2 [CX3011]  
uPD78F1818GBA [CX3011]  
uPD78F1819AGB [CX3011]  
uPD78F1819AGBA2 [CX3011]  
uPD78F1819GBA [CX3011]  
uPD78F1820AGB [CX3011]  
uPD78F1820AGBA2 [CX3011]  
uPD78F1820GBA [CX3011]  
uPD78F1821AGB [CX3011]  
uPD78F1821AGBA2 [CX3011]  
uPD78F1821GBA [CX3011]  
uPD78F1822AGB [CX3011]  
uPD78F1822AGBA2 [CX3011]  
uPD78F1822GBA [CX3011]  
uPD78F1823AGK [CX3016]  
uPD78F1823AGKA2 [CX3016]  
uPD78F1823GKA [CX3016]  
uPD78F1824AGK [CX3016]  
uPD78F1824AGKA2 [CX3016]  
uPD78F1824GKA [CX3016]  
uPD78F1825AGK [CX3016]  
uPD78F1825AGKA2 [CX3016]  
uPD78F1825GKA [CX3016]  
uPD78F1826AGA [CX3007]  
uPD78F1826AGAA2 [CX3007]  
uPD78F1826AK8A [CX3007]  
uPD78F1826GA [CX3007]  
uPD78F1826GAA2 [CX3007]  
uPD78F1826K8A [CX3007]  
uPD78F1827AGA [CX3007]  
uPD78F1827AGAA2 [CX3007]  
uPD78F1827AK8A [CX3007]  
uPD78F1827GA [CX3007]  
uPD78F1827GAA2 [CX3007]  
uPD78F1827K8A [CX3007]  
uPD78F1828AGA [CX3007]  
uPD78F1828AGAA2 [CX3007]  
uPD78F1828AK8A [CX3007]  
uPD78F1828GA [CX3007]  
uPD78F1828GAA2 [CX3007]  
uPD78F1828K8A [CX3007]  
uPD78F1829AGA [CX3007]  
uPD78F1829AGAA2 [CX3007]  
uPD78F1829AK8A [CX3007]  
uPD78F1829GA [CX3007]

uPD78F1815K8A2 [CX3007]  
uPD78F1816AGAA [CX3007]  
uPD78F1816AK8 [CX3007]  
uPD78F1816AK8A2 [CX3007]  
uPD78F1816GAA [CX3007]  
uPD78F1816K8 [CX3007]  
uPD78F1816K8A2 [CX3007]  
uPD78F1817AGAA [CX3007]  
uPD78F1817AK8 [CX3007]  
uPD78F1817AK8A2 [CX3007]  
uPD78F1817GAA [CX3007]  
uPD78F1817K8 [CX3007]  
uPD78F1817K8A2 [CX3007]  
uPD78F1818AGBA [CX3011]  
uPD78F1818GB [CX3011]  
uPD78F1818GBA2 [CX3011]  
uPD78F1819AGBA [CX3011]  
uPD78F1819GB [CX3011]  
uPD78F1819GBA2 [CX3011]  
uPD78F1820AGBA [CX3011]  
uPD78F1820GB [CX3011]  
uPD78F1820GBA2 [CX3011]  
uPD78F1821AGBA [CX3011]  
uPD78F1821GB [CX3011]  
uPD78F1821GBA2 [CX3011]  
uPD78F1822AGBA [CX3011]  
uPD78F1822GB [CX3011]  
uPD78F1822GBA2 [CX3011]  
uPD78F1823AGKA [CX3016]  
uPD78F1823GK [CX3016]  
uPD78F1823GKA2 [CX3016]  
uPD78F1824AGKA [CX3016]  
uPD78F1824GK [CX3016]  
uPD78F1824GKA2 [CX3016]  
uPD78F1825AGKA [CX3016]  
uPD78F1825GK [CX3016]  
uPD78F1825GKA2 [CX3016]  
uPD78F1826AGAA [CX3007]  
uPD78F1826AK8 [CX3007]  
uPD78F1826AK8A2 [CX3007]  
uPD78F1826GAA [CX3007]  
uPD78F1826K8 [CX3007]  
uPD78F1826K8A2 [CX3007]  
uPD78F1827AGAA [CX3007]  
uPD78F1827AK8 [CX3007]  
uPD78F1827AK8A2 [CX3007]  
uPD78F1827GAA [CX3007]  
uPD78F1827K8 [CX3007]  
uPD78F1827K8A2 [CX3007]  
uPD78F1828AGAA [CX3007]  
uPD78F1828AK8 [CX3007]  
uPD78F1828AK8A2 [CX3007]  
uPD78F1828GAA [CX3007]  
uPD78F1828K8 [CX3007]  
uPD78F1828K8A2 [CX3007]  
uPD78F1829AGAA [CX3007]  
uPD78F1829AK8 [CX3007]  
uPD78F1829AK8A2 [CX3007]  
uPD78F1829GAA [CX3007]



uPD78F1829GAA2 [CX3007]  
uPD78F1829K8A [CX3007]  
uPD78F1830AGA [CX3007]  
uPD78F1830AGAA2 [CX3007]  
uPD78F1830AK8A [CX3007]  
uPD78F1830GA [CX3007]  
uPD78F1830GAA2 [CX3007]  
uPD78F1830K8A [CX3007]  
uPD78F1831AGB [CX3011]  
uPD78F1831AGBA2 [CX3011]  
uPD78F1831GBA [CX3011]  
uPD78F1832AGB [CX3011]  
uPD78F1832AGBA2 [CX3011]  
uPD78F1832GBA [CX3011]  
uPD78F1833AGB [CX3011]  
uPD78F1833AGBA2 [CX3011]  
uPD78F1833GBA [CX3011]  
uPD78F1834AGB [CX3011]  
uPD78F1834AGBA2 [CX3011]  
uPD78F1834GBA [CX3011]  
uPD78F1835AGB [CX3011]  
uPD78F1835AGBA2 [CX3011]  
uPD78F1835GBA [CX3011]  
uPD78F1836AGK [CX3016]  
uPD78F1836AGKA2 [CX3016]  
uPD78F1836GKA [CX3016]  
uPD78F1837AGK [CX3016]  
uPD78F1837AGKA2 [CX3016]  
uPD78F1837GKA [CX3016]  
uPD78F1838AGK [CX3016]  
uPD78F1838AGKA2 [CX3016]  
uPD78F1838GKA [CX3016]  
uPD78F1839AGK [CX3016]  
uPD78F1839AGKA2 [CX3016]  
uPD78F1839GKA [CX3016]  
uPD78F1840AGK [CX3021]  
uPD78F1840AGKA2 [CX3021]  
uPD78F1840GKA [CX3021]  
uPD78F1841AGK [CX3021]  
uPD78F1841AGKA2 [CX3021]  
uPD78F1841GKA [CX3021]  
uPD78F1842AGK [CX3021]  
uPD78F1842AGKA2 [CX3021]  
uPD78F1842GKA [CX3021]  
uPD78F1843AGK [CX3021]  
uPD78F1843AGKA2 [CX3021]  
uPD78F1843GKA [CX3021]  
uPD78F1844AGK [CX3021]  
uPD78F1844AGKA2 [CX3021]  
uPD78F1844GKA [CX3021]  
uPD78F1845AGK [CX3021]  
uPD78F1845AGKA2 [CX3021]  
uPD78F1845GKA [CX3021]  
uPD78F9025@SDIP42 [CX0042]  
uPD78F9025A@SDIP42 [CX0042]  
uPD78F9025B@SDIP42 [CX0042]  
uPD78F9026@SDIP42 [CX0042]  
uPD78F9026A@SDIP42 [CX0042]  
uPD78F9026B@SDIP42 [CX0042]  
uPD78F1829K8 [CX3007]  
uPD78F1829K8A2 [CX3007]  
uPD78F1830AGAA [CX3007]  
uPD78F1830AK8 [CX3007]  
uPD78F1830AK8A2 [CX3007]  
uPD78F1830GAA [CX3007]  
uPD78F1830K8 [CX3007]  
uPD78F1830K8A2 [CX3007]  
uPD78F1831AGBA [CX3011]  
uPD78F1831GB [CX3011]  
uPD78F1831GBA2 [CX3011]  
uPD78F1832AGBA [CX3011]  
uPD78F1832GB [CX3011]  
uPD78F1832GBA2 [CX3011]  
uPD78F1833AGBA [CX3011]  
uPD78F1833GB [CX3011]  
uPD78F1833GBA2 [CX3011]  
uPD78F1834AGBA [CX3011]  
uPD78F1834GB [CX3011]  
uPD78F1834GBA2 [CX3011]  
uPD78F1835AGBA [CX3011]  
uPD78F1835GB [CX3011]  
uPD78F1835GBA2 [CX3011]  
uPD78F1836AGKA [CX3016]  
uPD78F1836GK [CX3016]  
uPD78F1836GKA2 [CX3016]  
uPD78F1837AGKA [CX3016]  
uPD78F1837GK [CX3016]  
uPD78F1837GKA2 [CX3016]  
uPD78F1838AGKA [CX3016]  
uPD78F1838GK [CX3016]  
uPD78F1838GKA2 [CX3016]  
uPD78F1839AGKA [CX3016]  
uPD78F1839GK [CX3016]  
uPD78F1839GKA2 [CX3016]  
uPD78F1840AGKA [CX3021]  
uPD78F1840GK [CX3021]  
uPD78F1840GKA2 [CX3021]  
uPD78F1841AGKA [CX3021]  
uPD78F1841GK [CX3021]  
uPD78F1841GKA2 [CX3021]  
uPD78F1842AGKA [CX3021]  
uPD78F1842GK [CX3021]  
uPD78F1842GKA2 [CX3021]  
uPD78F1843AGKA [CX3021]  
uPD78F1843GK [CX3021]  
uPD78F1843GKA2 [CX3021]  
uPD78F1844AGKA [CX3021]  
uPD78F1844GK [CX3021]  
uPD78F1844GKA2 [CX3021]  
uPD78F1845AGKA [CX3021]  
uPD78F1845GK [CX3021]  
uPD78F1845GKA2 [CX3021]  
uPD78F9025@TQFP44 [CX3002]  
uPD78F9025A@TQFP44 [CX3002]  
uPD78F9025B@TQFP44 [CX3002]  
uPD78F9026@TQFP44 [CX3002]  
uPD78F9026A@TQFP44 [CX3002]  
uPD78F9026B@TQFP44 [CX3002]

uPD78F9045@SDIP42 [CX0042]  
uPD78F9045A@SDIP42 [CX0042]  
uPD78F9045B@SDIP42 [CX0042]  
uPD78F9046@SDIP42 [CX0042]  
uPD78F9046A@SDIP42 [CX0042]  
uPD78F9046B@SDIP42 [CX0042]  
uPD78F9076@SSOP30 [CX1027]  
uPD78F9076AMC@SSOP30 [CX1027]  
uPD78F9116 [CX0001]  
uPD78F9116A [CX0001]  
uPD78F9116B [CX0001]  
uPD78F9136 [CX0001]  
uPD78F9136A [CX0001]  
uPD78F9136B [CX0001]  
uPD78F9189@SDIP32 [CX0032]  
uPD78F9200(A)@SSOP10 [CX1000]  
uPD78F9200@SSOP10 [CX1000]  
uPD78F9201(A2)@SSOP10 [CX1000]  
uPD78F9202(A)@SSOP10 [CX1000]  
uPD78F9202@SSOP10 [CX1000]  
uPD78F9210(A2)@SSOP16 [CX1000]  
uPD78F9211(A)@SSOP16 [CX1000]  
uPD78F9211@SSOP16 [CX1000]  
uPD78F9212(A2)@SSOP16 [CX1000]  
uPD78F9221(A)@SSOP20 [CX1027]  
uPD78F9221@SSOP20 [CX1027]  
uPD78F9222(A2)@SSOP20 [CX1027]  
uPD78F9224(A)@SSOP20 [CX1027]  
uPD78F9224@SSOP20 [CX1027]  
uPD78F9232(A)@SSOP30 [CX1027]  
uPD78F9232(A2)@SSOP30 [CX1027]  
uPD78F9232@SSOP30 [CX1027]  
uPD78F9234(A)@SSOP30 [CX1027]  
uPD78F9234(A2)@SSOP30 [CX1027]  
uPD78F9234@SSOP30 [CX1027]  
uPD78F9500(A2)@SSOP10 [CX1000]  
uPD78F9501(A)@SSOP10 [CX1000]  
uPD78F9501@SSOP10 [CX1000]  
uPD78F9502(A2)@SSOP10 [CX1000]  
uPD78F9510(A)@SSOP16 [CX1000]  
uPD78F9510@SSOP16 [CX1000]  
uPD78F9511(A2)@SSOP16 [CX1000]  
uPD78F9512(A)@SSOP16 [CX1000]  
uPD78F9512@SSOP16 [CX1000]  
uPD78F9521(A2)@SSOP20 [CX1027]  
uPD78F9522(A)@SSOP20 [CX1027]  
uPD78F9522@SSOP20 [CX1027]  
uPD78F9524(A2)@SSOP20 [CX1027]  
uPD78F9532(A)@SDIP32 [CX0032]  
uPD78F9532(A2)@SDIP32 [CX0032]  
uPD78F9532@SDIP32 [CX0032]  
uPD78F9534(A)@SDIP32 [CX0032]  
uPD78F9534(A2)@SDIP32 [CX0032]  
uPD78F9534@SDIP32 [CX0032]  
uPD78P9014CT@SDIP28 [CX0032]  
uPD79F7020CT [CX0032]  
uPD79F7020GB [CX3010]  
uPD79F7021CTA [CX0032]  
uPD79F7022CTA [CX0032]

uPD78F9045@TQFP44 [CX3002]  
uPD78F9045A@TQFP44 [CX3002]  
uPD78F9045B@TQFP44 [CX3002]  
uPD78F9046@TQFP44 [CX3002]  
uPD78F9046A@TQFP44 [CX3002]  
uPD78F9046B@TQFP44 [CX3002]  
uPD78F9076A@SSOP30 [CX1027]  
uPD78F9076MC@SSOP30 [CX1027]  
uPD78F9116@SSOP30 [CX1027]  
uPD78F9116A@SSOP30 [CX1027]  
uPD78F9116B@SSOP30 [CX1027]  
uPD78F9136@SSOP30 [CX1027]  
uPD78F9136A@SSOP30 [CX1027]  
uPD78F9136B@SSOP30 [CX1027]  
uPD78F9189CT@SDIP32 [CX0032]  
uPD78F9200(A2)@SSOP10 [CX1000]  
uPD78F9201(A)@SSOP10 [CX1000]  
uPD78F9201@SSOP10 [CX1000]  
uPD78F9202(A2)@SSOP10 [CX1000]  
uPD78F9210(A)@SSOP16 [CX1000]  
uPD78F9210@SSOP16 [CX1000]  
uPD78F9211(A2)@SSOP16 [CX1000]  
uPD78F9212(A)@SSOP16 [CX1000]  
uPD78F9212@SSOP16 [CX1000]  
uPD78F9221(A2)@SSOP20 [CX1027]  
uPD78F9222(A)@SSOP20 [CX1027]  
uPD78F9222@SSOP20 [CX1027]  
uPD78F9224(A2)@SSOP20 [CX1027]  
uPD78F9232(A)@SDIP32 [CX0032]  
uPD78F9232(A2)@SDIP32 [CX0032]  
uPD78F9232@SDIP32 [CX0032]  
uPD78F9234(A)@SDIP32 [CX0032]  
uPD78F9234(A2)@SDIP32 [CX0032]  
uPD78F9234@SDIP32 [CX0032]  
uPD78F9500(A)@SSOP10 [CX1000]  
uPD78F9500@SSOP10 [CX1000]  
uPD78F9501(A2)@SSOP10 [CX1000]  
uPD78F9502(A)@SSOP10 [CX1000]  
uPD78F9502@SSOP10 [CX1000]  
uPD78F9510(A2)@SSOP16 [CX1000]  
uPD78F9511(A)@SSOP16 [CX1000]  
uPD78F9511@SSOP16 [CX1000]  
uPD78F9512(A2)@SSOP16 [CX1000]  
uPD78F9521(A)@SSOP20 [CX1027]  
uPD78F9521@SSOP20 [CX1027]  
uPD78F9522(A2)@SSOP20 [CX1027]  
uPD78F9524(A)@SSOP20 [CX1027]  
uPD78F9524@SSOP20 [CX1027]  
uPD78F9532(A)@SSOP30 [CX1027]  
uPD78F9532(A2)@SSOP30 [CX1027]  
uPD78F9532@SSOP30 [CX1027]  
uPD78F9534(A)@SSOP30 [CX1027]  
uPD78F9534(A2)@SSOP30 [CX1027]  
uPD78F9534@SSOP30 [CX1027]  
uPD78P9014GT@SOIC28 [CX1033]  
uPD79F7020CTA [CX0032]  
uPD79F7021CT [CX0032]  
uPD79F7022CT [CX0032]  
uPD79F7023CT [CX0032]

uPD79F7023CTA [CX0032]  
UPD79F7024MC [CX1074]  
UPD79F7026@QFP32 [CX3001]  
uPD79F8200(A2)@SSOP10 [CX1000]  
uPD79F8201(A)@SSOP10 [CX1000]  
uPD79F8201@SSOP10 [CX1000]  
uPD79F8202(A2)@SSOP10 [CX1000]  
uPD79F8210(A)@SSOP16 [CX1000]  
uPD79F8210@SSOP16 [CX1000]  
uPD79F8211(A2)@SSOP16 [CX1000]  
uPD79F8212(A)@SSOP16 [CX1000]  
uPD79F8212@SSOP16 [CX1000]  
uPD79F8221(A2)@SSOP20 [CX1027]  
uPD79F8222(A)@SSOP20 [CX1027]  
uPD79F8222@SSOP20 [CX1027]  
uPD79F8224(A2)@SSOP20 [CX1027]  
uPD79F8232(A)@SDIP32 [CX0032]  
uPD79F8232(A2)@SDIP32 [CX0032]  
uPD79F8232@SDIP32 [CX0032]  
uPD79F8234(A)@SDIP32 [CX0032]  
uPD79F8234(A2)@SDIP32 [CX0032]  
uPD79F8234@SDIP32 [CX0032]  
uPD79F8430GB@QFP52 [CX3010]  
uPD79F8432GB@QFP52 [CX3010]  
uPD79F8434GB@QFP52 [CX3010]  
uPD79F8452GB [CX3011]  
uPD79F8453GB [CX3011]  
uPD79F8454GB [CX3011]  
uPD79F8455GB [CX3011]  
uPD79F8456GB [CX3011]  
uPD79F8457GB [CX3011]  
uPD79F8500(A)@SSOP10 [CX1000]  
uPD79F8500@SSOP10 [CX1000]  
uPD79F8501(A2)@SSOP10 [CX1000]  
uPD79F8502(A)@SSOP10 [CX1000]  
uPD79F8502@SSOP10 [CX1000]  
uPD79F8510(A2)@SSOP16 [CX1000]  
uPD79F8511(A)@SSOP16 [CX1000]  
uPD79F8511@SSOP16 [CX1000]  
uPD79F8511AGB@QFP44 [CX3005]  
uPD79F8511GA@QFP48 [CX3047]  
uPD79F8511MC@SSOP38 [CX1027]  
uPD79F8512(A2)@SSOP16 [CX1000]  
uPD79F8512AGA@QFP48 [CX3047]  
uPD79F8512AMC@SSOP38 [CX1027]  
uPD79F8512GB@QFP44 [CX3005]  
uPD79F8513AGA@QFP48 [CX3047]  
uPD79F8513AMC@SSOP38 [CX1027]  
uPD79F8513GB@QFP44 [CX3005]  
uPD79F8514AGA@QFP48 [CX3047]  
uPD79F8514AMC@SSOP38 [CX1027]  
uPD79F8514GB@QFP44 [CX3005]  
uPD79F8515AGA@QFP48 [CX3047]  
uPD79F8515AMC@SSOP38 [CX1027]  
uPD79F8515GB@QFP44 [CX3005]  
uPD79F8521(A)@SSOP20 [CX1027]  
uPD79F8521@SSOP20 [CX1027]  
uPD79F8522(A2)@SSOP20 [CX1027]  
uPD79F8524(A)@SSOP20 [CX1027]

UPD79F7023MC [CX1074]  
UPD79F7025@QFP32 [CX3001]  
uPD79F8200(A)@SSOP10 [CX1000]  
uPD79F8200@SSOP10 [CX1000]  
uPD79F8201(A2)@SSOP10 [CX1000]  
uPD79F8202(A)@SSOP10 [CX1000]  
uPD79F8202@SSOP10 [CX1000]  
uPD79F8210(A2)@SSOP16 [CX1000]  
uPD79F8211(A)@SSOP16 [CX1000]  
uPD79F8211@SSOP16 [CX1000]  
uPD79F8212(A2)@SSOP16 [CX1000]  
uPD79F8221(A)@SSOP20 [CX1027]  
uPD79F8221@SSOP20 [CX1027]  
uPD79F8222(A2)@SSOP20 [CX1027]  
uPD79F8224(A)@SSOP20 [CX1027]  
uPD79F8224@SSOP20 [CX1027]  
uPD79F8232(A)@SSOP30 [CX1027]  
uPD79F8232(A2)@SSOP30 [CX1027]  
uPD79F8232@SSOP30 [CX1027]  
uPD79F8234(A)@SSOP30 [CX1027]  
uPD79F8234(A2)@SSOP30 [CX1027]  
uPD79F8234@SSOP30 [CX1027]  
uPD79F8431GB@QFP52 [CX3010]  
uPD79F8433GB@QFP52 [CX3010]  
uPD79F8435GB@QFP52 [CX3010]  
uPD79F8452GK [CX3012]  
uPD79F8453GK [CX3012]  
uPD79F8454GK [CX3012]  
uPD79F8455GK [CX3012]  
uPD79F8456GK [CX3012]  
uPD79F8457GK [CX3012]  
uPD79F8500(A2)@SSOP10 [CX1000]  
uPD79F8501(A)@SSOP10 [CX1000]  
uPD79F8501@SSOP10 [CX1000]  
uPD79F8502(A2)@SSOP10 [CX1000]  
uPD79F8510(A)@SSOP16 [CX1000]  
uPD79F8510@SSOP16 [CX1000]  
uPD79F8511(A2)@SSOP16 [CX1000]  
uPD79F8511AGA@QFP48 [CX3047]  
uPD79F8511AMC@SSOP38 [CX1027]  
uPD79F8511GB@QFP44 [CX3005]  
uPD79F8512(A)@SSOP16 [CX1000]  
uPD79F8512@SSOP16 [CX1000]  
uPD79F8512AGB@QFP44 [CX3005]  
uPD79F8512GA@QFP48 [CX3047]  
uPD79F8512MC@SSOP38 [CX1027]  
uPD79F8513AGB@QFP44 [CX3005]  
uPD79F8513GA@QFP48 [CX3047]  
uPD79F8513MC@SSOP38 [CX1027]  
uPD79F8514AGB@QFP44 [CX3005]  
uPD79F8514GA@QFP48 [CX3047]  
uPD79F8514MC@SSOP38 [CX1027]  
uPD79F8515AGB@QFP44 [CX3005]  
uPD79F8515GA@QFP48 [CX3047]  
uPD79F8515MC@SSOP38 [CX1027]  
uPD79F8521(A2)@SSOP20 [CX1027]  
uPD79F8522(A)@SSOP20 [CX1027]  
uPD79F8522@SSOP20 [CX1027]  
uPD79F8524(A2)@SSOP20 [CX1027]

uPD79F8524@SSOP20 [CX1027]	uPD79F8532(A)@SDIP32 [CX0032]
uPD79F8532(A)@SSOP30 [CX1027]	uPD79F8532(A2)@SDIP32 [CX0032]
uPD79F8532(A2)@SSOP30 [CX1027]	uPD79F8532@SDIP32 [CX0032]
uPD79F8532@SSOP30 [CX1027]	uPD79F8534(A)@SDIP32 [CX0032]
uPD79F8534(A)@SSOP30 [CX1027]	uPD79F8534(A2)@SDIP32 [CX0032]
uPD79F8534(A2)@SSOP30 [CX1027]	uPD79F8534@SDIP32 [CX0032]
uPD79F8534@SSOP30 [CX1027]	uPD79F9201MC [CX1027]
uPD79F9203MC [CX1027]	uPD79F9204MC [CX1027]
uPD79F9205MC [CX1027]	uPD79F9211GA [CX3007]
uPD79F9211GB [CX3003]	uPD79F9211MC [CX1027]
uPD79F9213GA [CX3007]	uPD79F9213GB [CX3003]
uPD79F9213MC [CX1027]	uPD79F9214GA [CX3007]
uPD79F9214GB [CX3003]	uPD79F9214MC [CX1027]
uPD79F9215GA [CX3007]	uPD79F9215GB [CX3003]
uPD79F9215MC [CX1027]	uPD79F9221GB [CX3009]
uPD79F9223GB [CX3009]	uPD79F9224GB [CX3009]
uPD79F9225GB [CX3009]	uPD79F9231GB [CX3011]
uPD79F9231GK [CX3064]	uPD79F9233GB [CX3011]
uPD79F9233GK [CX3064]	uPD79F9234GB [CX3011]
uPD79F9234GK [CX3064]	uPD79F9235GB [CX3011]
uPD79F9235GK [CX3064]	

## NEXFLASH

### E (E) PROM/FRAM/NVRAM

NX25B40(Bottom Boot)@MLP8 [CX4005#1]	
NX25B40(Bottom Boot)@SOIC8 [CX1045#1]	
NX25B40(Top Boot)@MLP8 [CX4005#1]	
NX25B40(Top Boot)@SOIC8 [CX1045#1]	
NX25P10@MLP8 [CX4005]	NX25P10@SOIC8 [CX1045]
NX25P16@MLP8 [CX4005#1]	NX25P16@MLP8(ISP) [CX0001]
NX25P16@SOIC16 [CX1033#1]	NX25P16@SOIC16(ISP) [CX0001]
NX25P16@SOIC8 [CX1044#1]	NX25P16@SOIC8(ISP) [CX0001]
NX25P20@MLP8 [CX4005#1]	NX25P20@SOIC8 [CX1045#1]
NX25P32@MLP8 [CX1044#1]	NX25P32@MLP8(ISP) [CX0001]
NX25P32@SOIC16 [CX1033#1]	NX25P32@SOIC16(ISP) [CX0001]
NX25P40@MLP8 [CX4005#1]	NX25P40@SOIC8 [CX1045#1]
NX25P64@MLP8 [CX4005#1]	NX25P64@MLP8(ISP) [CX0001]
NX25P64@SOIC16 [CX1033#1]	NX25P64@SOIC16(ISP) [CX0001]
NX25P80@MLP8 [CX4005#1]	NX25P80@SOIC8 [CX1045#1]
NX29F010 [CX0001]	NX29F010@PLCC32 [CX2032]
NX29F010@TSOP32 [CX1002]	

## NJRC

### E (E) PROM/FRAM/NVRAM

NJU26040V [CX0001]	NJU26040V@SSOP32 [CX1026]
--------------------	---------------------------

## NORDIC

### MICROCONTROLLER

NRF24LE1@QFN24 [CX4012]	NRF24LE1@QFN32 [CX4015]
NRF24LE1@QFN48 [CX4021]	NRF24LE1D@QFN24 [CX4012]

NRF24LE1E@QFN32 [CX4015]  
NRF24LE1E@QFN32(fullrich) [CX4015]  
NRF24LE1F@QFN48 [CX4021]  
NRF24LE1-F16@QFN32 [CX4015]  
NRF24LE1G@QFN32 [CX4015]  
NRF24LE1I@QFN24 [CX4012]  
NRF24LE1-O17@QFN32 [CX4015]  
NRF24LE1-O17@QFN32(fullrich) [CX4015]  
NRF24LE1-O17@QFN48 [CX4021]  
NRF24LU1-F16@QFN32 [CX4015]  
NRF24LU1P-F16@QFN32 [CX4015]  
NRF24LU1P-O17@QFN32 [CX4015]  
nRF31512@QFN32 [CX4015]  
nRF31512C@QFN32 [CX4015]  
nRF31562A@QFN24 [CX4012]  
NRF24LE1-F16@QFN24 [CX4012]  
NRF24LE1-F16@QFN48 [CX4021]  
NRF24LE1H@QFN48 [CX4021]  
NRF24LE1-O17@QFN24 [CX4012]  
NRF24LU1@QFN32 [CX4015]  
NRF24LU1P@QFN32 [CX4015]  
NRF24LU1P-F32@QFN32 [CX4015]  
nRF31512@QFN28 [CX4033]  
nRF31512C@QFN28 [CX4033]  
nRF31562@QFN24 [CX4012]  
NRFLU1P16@QFN32 [CX4015]

## NOVATEK

### MICROCONTROLLER

NT68F631@PLCC44 [CX2044]  
NT68F631ALG@PLCC44 [CX2044]  
NT68F631L@PLCC44 [CX2044]  
NT68F631U@SDIP42 [CX0042]  
NT68F632@PLCC44 [CX2044]  
NT68F632ALG@PLCC44 [CX2044]  
NT68F632L@PLCC44 [CX2044]  
NT68F632U@SDIP42 [CX0042]  
NT68F633@PLCC44 [CX2044]  
NT68F633L@PLCC44 [CX2044]  
NT68F633U@SDIP42 [CX0042]  
NT68F636@PLCC44 [CX2044]  
NT68F636L@PLCC44 [CX2044]  
NT68F636U@SDIP42 [CX0042]  
NT68F63L(0444)@PLCC44 [CX2044]  
NT68F63L(0448)@PLCC44 [CX2044]  
NT68F63L(0523)@PLCC44 [CX2044]  
NT68F63L@PLCC44 [CX2044]  
NT68F63LG@PLCC44 [CX2044]  
NT68F63U@SDIP42 [CX0042]  
NT68F63UG@SDIP42 [CX0042]  
NT68F631@SDIP42 [CX0042]  
NT68F631AUG@SDIP42 [CX0042]  
NT68F631LG@PLCC44 [CX2044]  
NT68F631UG@SDIP42 [CX0042]  
NT68F632@SDIP42 [CX0042]  
NT68F632AUG@SDIP42 [CX0042]  
NT68F632LG@PLCC44 [CX2044]  
NT68F632UG@SDIP42 [CX0042]  
NT68F633@SDIP42 [CX0042]  
NT68F633LG@PLCC44 [CX2044]  
NT68F633UG@SDIP42 [CX0042]  
NT68F636@SDIP42 [CX0042]  
NT68F636LG@PLCC44 [CX2044]  
NT68F636UG@SDIP42 [CX0042]  
NT68F63L(0444)@SDIP42 [CX0042]  
NT68F63L(0448)@SDIP42 [CX0042]  
NT68F63L(0523)@SDIP42 [CX0042]  
NT68F63LA@PLCC44 [CX2044]  
NT68F63LGG@PLCC44 [CX2044]  
NT68F63UA@SDIP42 [CX0042]  
NT68F63UGG@SDIP42 [CX0042]

## NSC

### E(E) PROM/FRAM/NVRAM

2864 [CX0001]  
MM2716E [CX0001]  
NM24C02@SOIC8 [CX1045]  
NM24C02L [CX0001]  
NM24C02L@TSOP8 [CX1059]  
NM24C03@SOIC8 [CX1045]  
NM24C04 [CX0001]  
NM24C04@TSOP8 [CX1059]  
NM24C05@SOIC8 [CX1045]  
NM24C08 [CX0001]  
NM24C09 [CX0001]  
MM2716 [CX0001]  
NM24C02 [CX0001]  
NM24C02@TSOP8 [CX1059]  
NM24C02L@SOIC8 [CX1045]  
NM24C03 [CX0001]  
NM24C03@TSOP8 [CX1059]  
NM24C04@SOIC8 [CX1045]  
NM24C05 [CX0001]  
NM24C05@TSOP8 [CX1059]  
NM24C08@SOIC8 [CX1045]  
NM24C09@SOIC8 [CX1045]

NM24C16 [CX0001]  
NM24C17 [CX0001]  
NM27C010 [CX0001]  
NM27C010@TSOP32 [CX1002]  
NM27C010Q@PLCC32 [CX2032]  
NM27C020 [CX0001]  
NM27C020@TSOP32 [CX1002]  
NM27C020Q@PLCC32 [CX2032]  
NM27C040 [CX0001]  
NM27C040@TSOP32 [CX1002]  
NM27C128 [CX0001]  
NM27C210 [CX0001]  
NM27C210Q [CX0001]  
NM27C240 [CX0001]  
NM27C256 [CX0001]  
NM27C400 [CX0001]  
NM27C512@PLCC32 [CX2032]  
NM27C512Q@PLCC32 [CX2032]  
NM27C64Q@PLCC32 [CX2032]  
NM27CP256@PLCC32 [CX2032]  
NM27LC010@PLCC32 [CX2032]  
NM27LC256 [CX0001]  
NM27LC512 [CX0001]  
NM27LC64 [CX0001]  
NM27LV010 [CX0001]  
NM27LV010@TSOP32 [CX1002]  
NM27LV210@PLCC44 [CX2044]  
NM27LV512@PLCC32 [CX2032]  
NM27P040 [CX0001]  
NM27P040@TSOP32 [CX1002]  
NM27P210@PLCC44 [CX2044]  
NM27P512@PLCC32 [CX2032]  
NM59C11@SOIC8 [CX1045]  
NM93C06(08bit)@SOIC8 [CX1045]  
NM93C06(16bit)@SOIC8 [CX1045]  
NM93C46@SOIC8 [CX1045]  
NM93C46A(08bit)@SOIC8 [CX1045]  
NM93C46A(16bit)@SOIC8 [CX1045]  
NM93C46AL(08bit)@SOIC8 [CX1045]  
NM93C46AL(16bit)@SOIC8 [CX1045]  
NM93C46ALZ(08bit)@SOIC8 [CX1045]  
NM93C46ALZ(16bit)@SOIC8 [CX1045]  
NM93C46L@SOIC8 [CX1045]  
NM93C46LZ@SOIC8 [CX1045]  
NM93C56@SOIC8 [CX1045]  
NM93C56A(08bit)@SOIC8 [CX1045]  
NM93C56A(16bit)@SOIC8 [CX1045]  
NM93C56AL(08bit)@SOIC8 [CX1045]  
NM93C56AL(16bit)@SOIC8 [CX1045]  
NM93C56ALZ(08bit)@SOIC8 [CX1045]  
NM93C56ALZ(16bit)@SOIC8 [CX1045]  
NM93C56L@SOIC8 [CX1045]  
NM93C56LZ@SOIC8 [CX1045]  
NM93C66@SOIC8 [CX1045]  
NM93C66A(08bit) [CX0001]  
NM93C66A@SOIC8 [CX1045]  
NM93C66AL(08bit)@SOIC8 [CX1045]  
NM93C66AL(16bit)@SOIC8 [CX1045]  
NM93C66ALZ(08bit)@SOIC8 [CX1045]  
NM24C16@SOIC8 [CX1045]  
NM24C17@SOIC8 [CX1045]  
NM27C010@PLCC32 [CX2032]  
NM27C010Q [CX0001]  
NM27C010Q@TSOP32 [CX1002]  
NM27C020@PLCC32 [CX2032]  
NM27C020Q [CX0001]  
NM27C020Q@TSOP32 [CX1002]  
NM27C040@PLCC32 [CX2032]  
NM27C1023 [CX0001]  
NM27C128@PLCC32 [CX2032]  
NM27C210@PLCC44 [CX2044]  
NM27C210Q@PLCC44 [CX2044]  
NM27C240@PLCC44 [CX2044]  
NM27C256@PLCC32 [CX2032]  
NM27C512 [CX0001]  
NM27C512Q [CX0001]  
NM27C64Q [CX0001]  
NM27CP256 [CX0001]  
NM27LC010 [CX0001]  
NM27LC010@TSOP32 [CX1002]  
NM27LC256@PLCC32 [CX2032]  
NM27LC512@PLCC32 [CX2032]  
NM27LC64@PLCC32 [CX2032]  
NM27LV010@PLCC32 [CX2032]  
NM27LV210 [CX0001]  
NM27LV512 [CX0001]  
NM27LV512@TSOP32 [CX1002]  
NM27P040@PLCC32 [CX2032]  
NM27P210 [CX0001]  
NM27P512 [CX0001]  
NM59C11 [CX0001]  
NM93C06(08bit) [CX0001]  
NM93C06(16bit) [CX0001]  
NM93C46 [CX0001]  
NM93C46A(08bit) [CX0001]  
NM93C46A(16bit) [CX0001]  
NM93C46AL(08bit) [CX0001]  
NM93C46AL(16bit) [CX0001]  
NM93C46ALZ(08bit) [CX0001]  
NM93C46ALZ(16bit) [CX0001]  
NM93C46L [CX0001]  
NM93C46LZ [CX0001]  
NM93C56 [CX0001]  
NM93C56A(08bit) [CX0001]  
NM93C56A(16bit) [CX0001]  
NM93C56AL(08bit) [CX0001]  
NM93C56AL(16bit) [CX0001]  
NM93C56ALZ(08bit) [CX0001]  
NM93C56ALZ(16bit) [CX0001]  
NM93C56L [CX0001]  
NM93C56LZ [CX0001]  
NM93C66 [CX0001]  
NM93C66A [CX0001]  
NM93C66A(08bit)@SOIC8 [CX1045]  
NM93C66AL(08bit) [CX0001]  
NM93C66AL(16bit) [CX0001]  
NM93C66ALZ(08bit) [CX0001]  
NM93C66ALZ(16bit) [CX0001]

NM93C66ALZ(16bit)@SOIC8 [CX1045]  
NM93C66L@SOIC8 [CX1045]  
NM93C66LZ@SOIC8 [CX1045]  
NM93C86(16bit)@SOIC8 [CX1045]  
NM93C86A(08bit) [CX0001]  
NM93C86A@SOIC8 [CX1045]  
NM93C86AL(08bit)@SOIC8 [CX1045]  
NM93C86AL(16bit)@SOIC8 [CX1045]  
NM93C86ALZ(08bit)@SOIC8 [CX1045]  
NM93C86ALZ(16bit)@SOIC8 [CX1045]  
NM93C86L@SOIC8 [CX1045]  
NM93C86LZ@SOIC8 [CX1045]  
NM93CS06(MT8)@TSSOP8 [CX1059]  
NM93CS46(M8)@SOIC8 [CX1045]  
NM93CS46(N) [CX0001]  
NM93CS56(MT8)@TSSOP8 [CX1059]  
NM93CS66(M8)@SOIC8 [CX1045]  
NM93CS66(N) [CX0001]  
NMC2732B [CX0001]  
NMC27C010 [CX0001]  
NMC27C010@TSOP32 [CX1002]  
NMC27C1024@PLCC44 [CX2044]  
NMC27C128B@PLCC32 [CX2032]  
NMC27C128BN@PLCC32 [CX2032]  
NMC27C128BQ@PLCC32 [CX2032]  
NMC27C128Q [CX0001]  
NMC27C16BQ [CX0001]  
NMC27C16H [CX0001]  
NMC27C16Q [CX0001]  
NMC27C210@PLCC44 [CX2044]  
NMC27C210Q@PLCC44 [CX2044]  
NMC27C256B@PLCC32 [CX2032]  
NMC27C256BQE [CX0001]  
NMC27C256Q [CX0001]  
NMC27C32 [CX0001]  
NMC27C32BQ [CX0001]  
NMC27C32EH [CX0001]  
NMC27C512 [CX0001]  
NMC27C512A [CX0001]  
NMC27C512AN [CX0001]  
NMC27C64 [CX0001]  
NMC27C64BN [CX0001]  
NMC27CP128 [CX0001]  
NMC27CP64 [CX0001]  
NMC59C11@SOIC8 [CX1045]  
NMC87C257Q@PLCC32 [CX2032]  
NMC87C257V@PLCC32 [CX2032]  
NMC9306@SOIC8 [CX1045]  
NMC9307@SOIC8 [CX1045]  
NMC9346@SOIC8 [CX1045]  
NMC93C56@SOIC14 [CX1016]  
NMC93C66 [CX0001]  
NMC93C86A [CX0001]  
NMC93C86A@SOIC8 [CX1045]  
NMC93CS06(N) [CX0001]  
NMC93CS46(N) [CX0001]  
NMC93CS56(N) [CX0001]  
NMC93CS66(N) [CX0001]  
NMC93S06(N) [CX0001]  
NM93C66L [CX0001]  
NM93C66LZ [CX0001]  
NM93C86(16bit) [CX0001]  
NM93C86A [CX0001]  
NM93C86A(08bit)@SOIC8 [CX1045]  
NM93C86AL(08bit) [CX0001]  
NM93C86AL(16bit) [CX0001]  
NM93C86ALZ(08bit) [CX0001]  
NM93C86ALZ(16bit) [CX0001]  
NM93C86L [CX0001]  
NM93C86LZ [CX0001]  
NM93CS06(M8)@SOIC8 [CX1045]  
NM93CS06(N) [CX0001]  
NM93CS46(MT8)@TSSOP8 [CX1059]  
NM93CS56(M8)@SOIC8 [CX1045]  
NM93CS56(N) [CX0001]  
NM93CS66(MT8)@TSSOP8 [CX1059]  
NMC2732 [CX0001]  
NMC2732H [CX0001]  
NMC27C010@PLCC32 [CX2032]  
NMC27C1024 [CX0001]  
NMC27C128B [CX0001]  
NMC27C128BN [CX0001]  
NMC27C128BQ [CX0001]  
NMC27C128CQ [CX0001]  
NMC27C16 [CX0001]  
NMC27C16BQE [CX0001]  
NMC27C16HQ [CX0001]  
NMC27C210 [CX0001]  
NMC27C210Q [CX0001]  
NMC27C256B [CX0001]  
NMC27C256BN [CX0001]  
NMC27C256BQM [CX0001]  
NMC27C256Q@PLCC32 [CX2032]  
NMC27C32B [CX0001]  
NMC27C32E [CX0001]  
NMC27C32H [CX0001]  
NMC27C512@PLCC32 [CX2032]  
NMC27C512A@PLCC32 [CX2032]  
NMC27C512AN@PLCC32 [CX2032]  
NMC27C64@PLCC32 [CX2032]  
NMC27C64N [CX0001]  
NMC27CP256 [CX0001]  
NMC59C11 [CX0001]  
NMC87C257Q [CX0001]  
NMC87C257V [CX0001]  
NMC9306 [CX0001]  
NMC9307 [CX0001]  
NMC9346 [CX0001]  
NMC93C56 [CX0001]  
NMC93C56@SOIC8 [CX1045]  
NMC93C66@SOIC14 [CX1016]  
NMC93C86A@SOIC14 [CX1016]  
NMC93CS06(M14)@SOIC14 [CX1016]  
NMC93CS46(M14)@SOIC14 [CX1016]  
NMC93CS56(M14)@SOIC14 [CX1016]  
NMC93CS66(M14)@SOIC14 [CX1016]  
NMC93S06(M14)@SOIC14 [CX1016]  
NMC9817 [CX0001]

NMC9817A [CX0001]  
NS9816A [CX0001]

NS2816A [CX0001]

## BPROM

DM54LS471 [CX0001]  
DM54S188 [CX0001]  
DM54S287 [CX0001]  
DM54S288 [CX0001]  
DM54S387 [CX0001]  
DM54S471 [CX0001]  
DM54S472 [CX0001]  
DM54S472A [CX0001]  
DM54S472B [CX0001]  
DM54S473 [CX0001]  
DM54S473A [CX0001]  
DM54S474 [CX0001]  
DM54S474B [CX0001]  
DM54S475A [CX0001]  
DM54S570A [CX0001]  
DM54S571A [CX0001]  
DM54S572 [CX0001]  
DM54S573 [CX0001]  
DM54S573B [CX0001]  
DM74LS471@PLCC20 [CX2020]  
DM74S188A [CX0001]  
DM74S287A [CX0001]  
DM74S288A [CX0001]  
DM74S387A [CX0001]  
DM74S471@PLCC20 [CX2020]  
DM74S472@PLCC20 [CX2020]  
DM74S472A@PLCC20 [CX2020]  
DM74S472B@PLCC20 [CX2020]  
DM74S473@PLCC20 [CX2020]  
DM74S473A@PLCC20 [CX2020]  
DM74S474A [CX0001]  
DM74S475 [CX0001]  
DM74S570 [CX0001]  
DM74S571 [CX0001]  
DM74S571B [CX0001]  
DM74S572A [CX0001]  
DM74S573A [CX0001]  
DM74S573B [CX0001]

DM54LS471@PLCC20 [CX2020]  
DM54S188A [CX0001]  
DM54S287A [CX0001]  
DM54S288A [CX0001]  
DM54S387A [CX0001]  
DM54S471@PLCC20 [CX2020]  
DM54S472@PLCC20 [CX2020]  
DM54S472A@PLCC20 [CX2020]  
DM54S472B@PLCC20 [CX2020]  
DM54S473@PLCC20 [CX2020]  
DM54S473A@PLCC20 [CX2020]  
DM54S474A [CX0001]  
DM54S475 [CX0001]  
DM54S570 [CX0001]  
DM54S571 [CX0001]  
DM54S571B [CX0001]  
DM54S572A [CX0001]  
DM54S573A [CX0001]  
DM74LS471 [CX0001]  
DM74S188 [CX0001]  
DM74S287 [CX0001]  
DM74S288 [CX0001]  
DM74S387 [CX0001]  
DM74S471 [CX0001]  
DM74S472 [CX0001]  
DM74S472A [CX0001]  
DM74S472B [CX0001]  
DM74S473 [CX0001]  
DM74S473A [CX0001]  
DM74S474 [CX0001]  
DM74S474B [CX0001]  
DM74S475A [CX0001]  
DM74S570A [CX0001]  
DM74S571A [CX0001]  
DM74S572 [CX0001]  
DM74S573 [CX0001]  
DM74S573B [CX0001]

## PLD

GAL16V8 [CX0001]  
GAL16V8A [CX0001]  
PAL10H8 [CX0001]  
PAL10H8A2 [CX0001]  
PAL10L8A [CX0001]  
PAL12H6 [CX0001]  
PAL12H6A2 [CX0001]  
PAL12L6A [CX0001]  
PAL14H4 [CX0001]  
PAL14H4A2 [CX0001]  
PAL14L4A [CX0001]  
PAL16C1 [CX0001]  
PAL16C1A2 [CX0001]

GAL16V8@PLCC20 [CX2020]  
GAL16V8A@PLCC20 [CX2020]  
PAL10H8A [CX0001]  
PAL10L8 [CX0001]  
PAL10L8A2 [CX0001]  
PAL12H6A [CX0001]  
PAL12L6 [CX0001]  
PAL12L6A2 [CX0001]  
PAL14H4A [CX0001]  
PAL14L4 [CX0001]  
PAL14L4A2 [CX0001]  
PAL16C1A [CX0001]  
PAL16H2 [CX0001]



PAL16H2A [CX0001]  
PAL16L2 [CX0001]  
PAL16L2A2 [CX0001]  
PAL16L8A2 [CX0001]  
PAL16L8B2 [CX0001]  
PAL16R4A [CX0001]  
PAL16R4B [CX0001]  
PAL16R6 [CX0001]  
PAL16R6A2 [CX0001]  
PAL16R6B2 [CX0001]  
PAL16R8A [CX0001]  
PAL16R8B [CX0001]

PAL16H2A2 [CX0001]  
PAL16L2A [CX0001]  
PAL16L8 [CX0001]  
PAL16L8B [CX0001]  
PAL16R4 [CX0001]  
PAL16R4A2 [CX0001]  
PAL16R4B2 [CX0001]  
PAL16R6A [CX0001]  
PAL16R6B [CX0001]  
PAL16R8 [CX0001]  
PAL16R8A2 [CX0001]  
PAL16R8B2 [CX0001]

## MICROCONTROLLER

COP820(CJMHD) [CX0001]  
COP822(CJMHD) [CX0001]  
COP8640(CMHD) [CX0001]  
COP8642(CMHD) [CX0001]  
COP8780(CEL)@PLCC44 [CX2044]  
COP8780(CN) [CX0001]  
COP8781(CD) [CX0001]  
COP8781(CMC)@SOIC28 [CX1033]  
COP8781(CWM)@SOIC28 [CX1033]  
COP8782(CJ) [CX0001]  
COP8782(CN) [CX0001]  
COP8784(CFN) [CX0001]  
COP8784(CLN) [CX0001]  
COP8784(EGN) [CX0001]  
COP8788(CFN) [CX0001]  
COP8788(CLN) [CX0001]  
COP8788(EGN) [CX0001]  
COP87L20 [CX0001]  
COP87L22 [CX0001]  
COP87L40 [CX0001]  
COP87L42 [CX0001]  
COP87L84 [CX0001]  
COP87L84BC [CX0001]  
COP87L88 [CX0001]  
COP87L88@PLCC68 [CX2068]  
COP87L88EB@PLCC44 [CX2044]  
COP87L88GW@PLCC68 [CX2068]  
COP880(CMHEL)@PLCC44 [CX2044]  
COP881(CMHEA)@SOIC28 [CX1033]  
COP884(CFMHEA)@SOIC28 [CX1033]  
COP884(CGMHEA)@SOIC28 [CX1033]  
COP884(CLMHEA)@SOIC28 [CX1033]  
COP884(CSMHEA)@SOIC28 [CX1033]  
COP884(EGMHEA)@SOIC28 [CX1033]  
COP888(CFMHEL)@PLCC44 [CX2044]  
COP888(CGMHEL)@PLCC44 [CX2044]  
COP888(CLMHEL)@PLCC44 [CX2044]  
COP888(CSMHEL)@PLCC44 [CX2044]  
COP888(EGMHEL)@PLCC44 [CX2044]  
COP8ACC720@SOIC20 [CX1033]  
COP8ACC728@SOIC28 [CX1033]  
COP8ALE728@SOIC28 [CX1033]  
COP8AXE9@SOIC28 [CX1033]  
COP8CBE9@TQFP44 [CX3002]

COP820(CJMHEA)@SOIC28 [CX1033]  
COP842(CMHD) [CX0001]  
COP8640(CMHEA)@SOIC28 [CX1033]  
COP8780(CD) [CX0001]  
COP8780(CJ) [CX0001]  
COP8780(CV)@PLCC44 [CX2044]  
COP8781(CJ) [CX0001]  
COP8781(CN) [CX0001]  
COP8782(CD) [CX0001]  
COP8782(CMC)@SOIC20 [CX1033]  
COP8782(CWM)@SOIC20 [CX1033]  
COP8784(CFWM) [CX0001]  
COP8784(CLWM) [CX0001]  
COP8784(EGWM) [CX0001]  
COP8788(CFV)@PLCC44 [CX2044]  
COP8788(CLV)@PLCC44 [CX2044]  
COP8788(EGV)@PLCC44 [CX2044]  
COP87L20@SOIC28 [CX1033]  
COP87L22@SOIC20 [CX1033]  
COP87L40@SOIC28 [CX1033]  
COP87L42@SOIC20 [CX1033]  
COP87L84@SOIC28 [CX1033]  
COP87L84BC@SOIC28 [CX1033]  
COP87L88@PLCC44 [CX2044]  
COP87L88@TQFP44 [CX3002]  
COP87L88EB@PLCC68 [CX2068]  
COP880(CMHD) [CX0001]  
COP881(CMHD) [CX0001]  
COP884(CFMHD) [CX0001]  
COP884(CGMHD) [CX0001]  
COP884(CLMHD) [CX0001]  
COP884(CSMHD) [CX0001]  
COP884(EGMHD) [CX0001]  
COP888(CFMHD) [CX0001]  
COP888(CGMHD) [CX0001]  
COP888(CLMHD) [CX0001]  
COP888(CSMHD) [CX0001]  
COP888(EGMHD) [CX0001]  
COP8ACC720 [CX0001]  
COP8ACC728 [CX0001]  
COP8ALE728 [CX0001]  
COP8AXE9 [CX0001]  
COP8CBE9@PLCC44 [CX2044]  
COP8CBR9@PLCC44 [CX2044]

COP8CBR9@PLCC68 [CX2068]  
COP8CCE9@PLCC44 [CX2044]  
COP8CCR9@PLCC44 [CX2044]  
COP8CCR9@TQFP44 [CX3002]  
COP8CDR9@PLCC68 [CX2068]  
COP8CXC9@PLCC44 [CX2044]  
COP8SAA716 [CX0001]  
COP8SAA720 [CX0001]  
COP8SAA728 [CX0001]  
COP8SAA728@SOIC28 [CX1033]  
COP8SAA740@SOIC40 [CX1014]  
COP8SAA744@TQFP44 [CX3002]  
COP8SAB716@SOIC16 [CX1033]  
COP8SAB720@SOIC20 [CX1033]  
COP8SAB728@PLCC28 [CX2028]  
COP8SAB740 [CX0001]  
COP8SAB744@PLCC44 [CX2044]  
COP8SAC716 [CX0001]  
COP8SAC720 [CX0001]  
COP8SAC728 [CX0001]  
COP8SAC728@SOIC28 [CX1033]  
COP8SAC740@SOIC40 [CX1014]  
COP8SAC744@TQFP44 [CX3002]  
COP8SBE9@PLCC68 [CX2068]  
COP8SBR9@PLCC68 [CX2068]  
COP8SCE9@PLCC44 [CX2044]  
COP8SCR9@PLCC44 [CX2044]  
COP8SCR9@TQFP44 [CX3002]  
COP8SDR9@PLCC68 [CX2068]  
COP8SGE720 [CX0001]  
COP8SGE728 [CX0001]  
COP8SGE740 [CX0001]  
COP8SGE744@PLCC44 [CX2044]  
COP8SGR720 [CX0001]  
COP8SGR728 [CX0001]  
COP8SGR740 [CX0001]  
COP8SGR744@PLCC44 [CX2044]  
COP943(CMHD) [CX0001]

COP8CBR9@TQFP44 [CX3002]  
COP8CCE9@TQFP44 [CX3002]  
COP8CCR9@PLCC68 [CX2068]  
COP8CDR9@PLCC44 [CX2044]  
COP8CDR9@TQFP44 [CX3002]  
COP8CXG9@PLCC44 [CX2044]  
COP8SAA716@SOIC16 [CX1033]  
COP8SAA720@SOIC20 [CX1033]  
COP8SAA728@PLCC28 [CX2028]  
COP8SAA740 [CX0001]  
COP8SAA744@PLCC44 [CX2044]  
COP8SAB716 [CX0001]  
COP8SAB720 [CX0001]  
COP8SAB728 [CX0001]  
COP8SAB728@SOIC28 [CX1033]  
COP8SAB740@SOIC40 [CX1014]  
COP8SAB744@TQFP44 [CX3002]  
COP8SAC716@SOIC16 [CX1033]  
COP8SAC720@SOIC20 [CX1033]  
COP8SAC728@PLCC28 [CX2028]  
COP8SAC740 [CX0001]  
COP8SAC744@PLCC44 [CX2044]  
COP8SBE9@PLCC44 [CX2044]  
COP8SBR9@PLCC44 [CX2044]  
COP8SBR9@TQFP44 [CX3002]  
COP8SCE9@PLCC68 [CX2068]  
COP8SCR9@PLCC68 [CX2068]  
COP8SDR9@PLCC44 [CX2044]  
COP8SDR9@TQFP44 [CX3002]  
COP8SGE720@SOIC20 [CX1033]  
COP8SGE728@SOIC28 [CX1033]  
COP8SGE740@SOIC40 [CX1014]  
COP8SGE744@TQFP44 [CX3002]  
COP8SGR720@SOIC20 [CX1033]  
COP8SGR728@SOIC28 [CX1033]  
COP8SGR740@SOIC40 [CX1014]  
COP8SGR744@TQFP44 [CX3002]

## NTE

### E (E) PROM/FRAM/NVRAM

NTE2532 [CX0001]  
NTE25L32 [CX0001]

NTE2532A [CX0001]

## NUMONYX

### E (E) PROM/FRAM/NVRAM

JR28F032M29EWB@TSOP48 [CX1004]  
JR28F032M29EWL@TSOP48 [CX1004]  
JR28F064M29EWB@TSOP48 [CX1004]  
JR28F064M29EWL@TSOP48 [CX1004]  
JS28F00AM29EWH@TSOP56 [CX1055]  
JS28F00AM29EWL@TSOP56 [CX1055]  
JS28F00AP30BF@TSOP56 [CX1011]

JR28F032M29EWH@TSOP48 [CX1004]  
JR28F032M29EWT@TSOP48 [CX1004]  
JR28F064M29EWH@TSOP48 [CX1004]  
JR28F064M29EWT@TSOP48 [CX1004]  
JS28F00AM29EWH@TSOP56 [CX1055]  
JS28F00AM29EWH@TSOP56 [CX1055]  
JS28F00AM29EWH@TSOP56 [CX1055]  
JS28F00AM29EWH@TSOP56 [CX1055]  
JS28F00AP30EF@TSOP56 [CX1011]

JS28F00AP30TF@TSOP56 [CX1011] JS28F00AP33BF@TSOP56 [CX1011]  
JS28F00AP33EF@TSOP56 [CX1011] JS28F00AP33TF@TSOP56 [CX1011]  
JS28F00BM29EWH@TSOP56 [CX1055] JS28F064M29EWB@TSOP56 [CX1055]  
JS28F064M29EWH@TSOP56 [CX1055] JS28F064M29EWL@TSOP56 [CX1055]  
JS28F064M29EWT@TSOP56 [CX1055] JS28F128J3F@TSOP56 [CX1011]  
JS28F128M29EWH@TSOP56 [CX1055] JS28F128M29EWL@TSOP56 [CX1055]  
JS28F128M29EWLD@TSOP56 [CX1055] JS28F128P30BF@TSOP56 [CX1011]  
JS28F128P30TF@TSOP56 [CX1011] JS28F128P33BF@TSOP56 [CX1011]  
JS28F128P33TF@TSOP56 [CX1011] JS28F256J3F@TSOP56 [CX1011]  
JS28F256M29EWH@TSOP56 [CX1055] JS28F256M29EWHS@TSOP56 [CX1055]  
JS28F256M29EWL@TSOP56 [CX1055] JS28F256M29EWLS@TSOP56 [CX1055]  
JS28F256P30BF@TSOP56 [CX1011] JS28F256P30TF@TSOP56 [CX1011]  
JS28F256P33BF@TSOP56 [CX1011] JS28F256P33TF@TSOP56 [CX1011]  
JS28F320J3F@TSOP56 [CX1011] JS28F512M29AWH@FBGA56 [CX1055]  
JS28F512M29AWL@FBGA56 [CX1055] JS28F512M29EWH@TSOP56 [CX1055]  
JS28F512M29EWS@TSOP56 [CX1055] JS28F512M29EWL@TSOP56 [CX1055]  
JS28F512M29EWLS@TSOP56 [CX1055] JS28F512P30BF@TSOP56 [CX1011]  
JS28F512P30EF@TSOP56 [CX1011] JS28F512P30TF@TSOP56 [CX1011]  
JS28F512P33BF@TSOP56 [CX1011] JS28F512P33EF@TSOP56 [CX1011]  
JS28F512P33TF@TSOP56 [CX1011] JS28F640J3F@TSOP56 [CX1011]  
JS28F640P30BF@TSOP56 [CX1011] JS28F640P30TF@TSOP56 [CX1011]  
JS28F640P33BF@TSOP56 [CX1011] JS28F640P33TF@TSOP56 [CX1011]  
M25P05-A@SO8 [CX1045#1] M25P05-A@TSSOP8 [CX1059#3]  
M25P05-A@UFD FPN8 [CX4002#1] M25P05-A@VFQFPN8 [CX4005#1]  
M25P10-A@SOIC8 [CX1045#1] M25P10-A@UFD FPN8 [CX4002#1]  
M25P10-A@VFQFPN8 [CX4005#1] M25P128@SO16 [CX1033#1]  
M25P128@VDFPN8 [CX4006#1] M25P20@QFN8L [CX4005#1]  
M25P20@SO8 [CX1045#1] M25P20@VFQFPN8 [CX4005#1]  
M25P40@DFN8 [CX4005#1] M25P40@SO8N [CX1045#1]  
M25P40@SO8W [CX1044#1] M25P40@VFDFPN8 [CX4005#1]  
M25P40MB@UFD FPN8 [CX4002#1] M25P40MC@UFD FPN8 [CX4076]  
M25P64@SO16 [CX1033#1] M25P64@VDFPN8 [CX4006#1]  
M25P80 [CX0001] M25P80@SOIC8(150 mil) [CX1045#1]  
M25P80@SOIC8(200 mil) [CX1044#1] M25P80@UFD FPN8 [CX4002#1]  
M25P80@VFDFPN8 [CX4005#1] M25PE10@SO8N [CX1045#1]  
M25PE10@VFQFPN8 [CX4005#1] M25PE16@SO8W [CX1044#1]  
M25PE16@VFQFPN8 [CX4005#1] M25PE20@SO8N [CX1045#1]  
M25PE20@VFQFPN8 [CX4005#1] M25PE40@SO8N [CX1045#1]  
M25PE40@SO8W [CX1044#1] M25PE40@VFQFPN8 [CX4005#1]  
M25PE80@QFN8L [CX4005#1] M25PE80@SO8N [CX1045#1]  
M25PE80@SO8W [CX1044#1] M25PE80@VFQFPN8 [CX4005#1]  
M25PX16@SOIC16 [CX1033#1] M25PX16@VFQFPN8 [CX4005#1]  
M25PX16@SOIC8(150 mil) [CX1045#1] M25PX32@SOIC8 [CX1044#1]  
M25PX16@SOIC8(200 mil) [CX1044#1] M25PX32@VFQFPN8 [CX4005#1]  
M25PX16@TBGA24 [CX5157] M25PX64@TBGA24 [CX5157]  
M25PX32@SOIC16 [CX1033#1] M25PX80 [CX0001#1]  
M25PX32@TBGA24 [CX5157] M28W320ECB@FBGA48 [CX5031]  
M25PX64@SOIC16 [CX1033#1] M28W320ECT@FBGA48 [CX5031]  
M25PX64@VDFPN8 [CX4006#1] M28W320FCB@FBGA48 [CX5031]  
M25PX80@SOIC8[150 mil] [CX1045#1] M28W320FCT@FBGA48 [CX5031]  
M25PX80@SOIC8[200 mil] [CX1044#1] M28W640ECB@FBGA48 [CX5078]  
M25PX80@VFQFPN8 [CX4005#1] M28W640ECT@FBGA48 [CX5078]  
M28W320ECB@TSOP48 [CX1004] M28W640FCB@FBGA48 [CX5078]  
M28W320ECT@TSOP48 [CX1004] M28W640FCT@FBGA48 [CX5078]  
M28W320FCB@TSOP48 [CX1004] M28W640FCT@FBGA48 [CX5078]  
M28W320FCT@TSOP48 [CX1004] M28W640FCT@FBGA48 [CX5078]  
M28W640ECB@TSOP48 [CX1004] M28W640FCT@FBGA48 [CX5078]  
M28W640ECT@TSOP48 [CX1004] M28W640FCT@FBGA48 [CX5078]  
M28W640FCB@TSOP48 [CX1004] M28W640FCT@FBGA48 [CX5078]

M28W640FCT@TSOP48 [CX1004]  
M28W640HCB@TSOP48 [CX1004]  
M28W640HCT@TSOP48 [CX1004]  
M29DW127G@TSOP56 [CX1011]  
M29DW128G@TSOP56 [CX1055]  
M29DW256G@TFBGA64 [CX5004]  
M29F160FB@FBGA48 [CX5002]  
M29F160FT@FBGA48 [CX5002]  
M29F200FB@FBGA48 [CX5002]  
M29F200FB@TSOP48 [CX1043]  
M29F200FT@PSOP44 [CX1014]  
M29F200FT@TSOP48 [CX1043]  
M29F400FB@FBGA48 [CX5002]  
M29F400FB@TSOP48 [CX1043]  
M29F400FT@PSOP44 [CX1014]  
M29F400FT@TSOP48 [CX1043]  
M29F800FB@FBGA48 [CX5002]  
M29F800FB@TSOP48 [CX1043]  
M29F800FT@PSOP44 [CX1014]  
M29W064FB@FBGA48 [CX5002]  
M29W064FT@FBGA48 [CX5002]  
M29W128GSH@FBGA64 [CX5004]  
M29W128GSH@TSOP56 [CX1055]  
M29W128GSL@FBGA64(ZS) [CX5074]  
M29W128GSL@TSOP56 [CX1055]  
M29W160DB@LBGA48 [CX5022]  
M29W160DB@TSOP48 [CX1004]  
M29W160DT@PSOP44 [CX1014]  
M29W160DT@TSOP48 [CX1004]  
M29W160EB@LBGA48 [CX5002]  
M29W160EB@PSOP44 [CX1014]  
M29W160EB@TSOP48 [CX1004]  
M29W160ET@LBGA48 [CX5002]  
M29W160ET@PSOP44 [CX1014]  
M29W160FB@LBGA48 [CX5002]  
M29W160FB@TSOP48 [CX1004]  
M29W160FT@LBGA48 [CX5002]  
M29W160FT@TSOP48 [CX1004]  
M29W256GH@LFBGA64 [CX5074]  
M29W256GH@TSOP56 [CX1055]  
M29W256GL@TFBGA64 [CX5004]  
M29W256GL@TSOP56 [CX1055]  
M29W320EB@FBGA48 [CX5002]  
M29W320EB@TSOP48 [CX1004]  
M29W320ET@FBGA48 [CX5002]  
M29W320ET@TSOP48 [CX1004]  
M29W400DB(ZA)@LBGA48 [CX5039]  
M29W400DB@PSOP44 [CX1014]  
M29W400DT(ZA)@LBGA48 [CX5039]  
M29W400DT@PSOP44 [CX1014]  
M29W400DT@TSOP48 [CX1004]  
M29W400FB@FBGA48 [CX5002]  
M29W400FB@TSOP48 [CX1004]  
M29W400FT@FBGA48 [CX5002]  
M29W400FT@TSOP48 [CX1004]  
M29W640DB@FBGA63 [CX5047]  
M29W640DB@TSOP48 [CX1004]  
M29W640DT@FBGA63 [CX5047]  
M29W640DT@TSOP48 [CX1004]  
M29W641DH@TSOP48 [CX1004]  
M29W641DL@TSOP48 [CX1004]  
M29W641DU@FBGA63 [CX5047]  
M29W800DB@PSOP44 [CX1014]  
M29W800DB@TSOP48 [CX1004]  
M29W800DT@FBGA48 [CX5002]  
M29W800DT@PSOP44 [CX1014]  
M29W800DT@TSOP48 [CX1004]  
M29W800FB@FBGA48 [CX5039]  
M29W800FT@FBGA48 [CX5039]  
M30L0R7000T0@FBGA88 [CX5005]  
M30L0R8000B0@FBGA88 [CX5005]  
M30L0R8000B2@FBGA88 [CX5005]  
M30L0R8000T0@FBGA88 [CX5005]  
M30L0R8000T2@FBGA88 [CX5005]  
M36C0W5030T0@FBGA56 [CX5045]  
M36C0W5040B0@FBGA56 [CX5045]  
M36C0W5040T0@FBGA56 [CX5045]  
M36C0W6040T0@FBGA56 [CX5045]  
M36C0W6050B0@FBGA56 [CX5045]  
M36L0R7040B0@FBGA88 [CX5005]  
M28W640HCB@FBGA48 [CX5078]  
M28W640HCT@FBGA48 [CX5078]  
M29DW127G@FBGA64 [CX5004]  
M29DW128G@FBGA64 [CX5004]  
M29DW256G@LFBGA64 [CX5074]  
M29DW256G@TSOP56 [CX1055]  
M29F160FB@TSOP48 [CX1043]  
M29F160FT@TSOP48 [CX1043]  
M29F200FB@PSOP44 [CX1014]  
M29F200FT@FBGA48 [CX5002]  
M29F200FT@TSOP48 [CX1043]  
M29F400FB@PSOP44 [CX1014]  
M29F400FT@FBGA48 [CX5002]  
M29F400FT@TSOP48 [CX1043]  
M29F800FB@PSOP44 [CX1014]  
M29F800FT@FBGA48 [CX5002]  
M29F800FT@TSOP48 [CX1043]  
M29W064FB@TSOP48 [CX1004]  
M29W064FT@TSOP48 [CX1004]  
M29W128GSH@FBGA64(ZS) [CX5074]  
M29W128GSL@FBGA64 [CX5004]  
M29W128GSL@TSOP56 [CX1055]  
M29W160DB@PSOP44 [CX1014]  
M29W160DT@LBGA48 [CX5022]  
M29W160DT@TSOP48 [CX1004]  
M29W160EB@LBGA64 [CX5074]  
M29W160EB@TSOP48 [CX1004]  
M29W160ET@LBGA64 [CX5074]  
M29W160ET@TSOP48 [CX1004]  
M29W160FB@TSOP48 [CX1004]  
M29W160FT@TSOP48 [CX1004]  
M29W256GH@TFBGA64 [CX5004]  
M29W256GL@LFBGA64 [CX5074]  
M29W256GL@TSOP56 [CX1055]  
M29W320EB@FBGA64 [CX5074]  
M29W320ET@FBGA48 [CX5002]  
M29W320ET@TSOP48 [CX1004]  
M29W400DB(ZE)@LBGA48 [CX5002]  
M29W400DB@TSOP48 [CX1004]  
M29W400DT(ZE)@LBGA48 [CX5002]  
M29W400DT@TSOP48 [CX1004]  
M29W400FB@TSOP48 [CX1004]  
M29W400FT@TSOP48 [CX1004]  
M29W640DB@TSOP48 [CX1004]  
M29W640DT@TSOP48 [CX1004]  
M29W641DL@TSOP48 [CX1004]  
M29W800DB@FBGA48 [CX5002]  
M29W800DB@TSOP48 [CX1004]  
M29W800DT@PSOP44 [CX1014]  
M29W800FB@FBGA48 [CX5039]  
M29W800FT@FBGA48 [CX5039]  
M30L0R7000B0@FBGA88 [CX5005]  
M30L0R8000B0@FBGA88 [CX5005]  
M30L0R8000T0@FBGA88 [CX5005]  
M36C0W5030B0@FBGA56 [CX5045]  
M36C0W5040B0@FBGA56 [CX5045]  
M36C0W6040B0@FBGA56 [CX5045]  
M36C0W6050B0@FBGA56 [CX5045]  
M36L0R7040B0@FBGA88 [CX5005]

M36L0R7040T0@FBGA88 [CX5005] M36L0R7050B0@FBGA88 [CX5005]  
M36L0R7050B1@FBGA88 [CX5005] M36L0R7050B2@FBGA88 [CX5005]  
M36L0R7050B3@FBGA80 [CX5052] M36L0R7050B4@FBGA80 [CX5052]  
M36L0R7050B4@FBGA88 [CX5005] M36L0R7050B4@FBGA88(MW) [CX5005]  
M36L0R7050B4@FBGA88(W) [CX5001] M36L0R7050L3@FBGA56 [CX5099]  
M36L0R7050L3@FBGA56(ZTE) [CX5186] M36L0R7050T0@FBGA88 [CX5005]  
M36L0R7050L3@FBGA88 [CX5005] M36L0R7050T2@FBGA88 [CX5005]  
M36L0R7050T1@FBGA88 [CX5005] M36L0R7050T4@FBGA80 [CX5052]  
M36L0R7050T3@FBGA80 [CX5052] M36L0R7050T4@FBGA88(MW) [CX5005]  
M36L0R7050T4@FBGA88 [CX5005]  
M36L0R7050U3@FBGA56 [CX5099]  
M36L0R7050U3@FBGA56(ZTE) [CX5186]  
M36L0R7050U3@FBGA88 [CX5005] M36L0R7060B1@FBGA88 [CX5005]  
M36L0R7060B2@FBGA88 [CX5005] M36L0R7060L3@FBGA56 [CX5099]  
M36L0R7060L3@FBGA88 [CX5005] M36L0R7060T1@FBGA88 [CX5005]  
M36L0R7060T2@FBGA88 [CX5005] M36L0R7060U3@FBGA56 [CX5099]  
M36L0R7060U3@FBGA88 [CX5005] M36L0R8050L3@FBGA56 [CX5099]  
M36L0R8050L3@FBGA88 [CX5005] M36L0R8050U3@FBGA56 [CX5099]  
M36L0R8050U3@FBGA88 [CX5005] M36L0R8060B0@FBGA88 [CX5005]  
M36L0R8060B1@FBGA88 [CX5005] M36L0R8060B3@FBGA88 [CX5005]  
M36L0R8060B5@FBGA88 [CX5005] M36L0R8060B8@FBGA88 [CX5005]  
M36L0R8060B9@FBGA88 [CX5005] M36L0R8060L3@FBGA56 [CX5099]  
M36L0R8060L3@FBGA80 [CX5052] M36L0R8060L3@FBGA88 [CX5005]  
M36L0R8060T0@FBGA88 [CX5005] M36L0R8060T1@FBGA88 [CX5005]  
M36L0R8060T3@FBGA88 [CX5005] M36L0R8060T5@FBGA88 [CX5005]  
M36L0R8060T8@FBGA88 [CX5005] M36L0R8060T9@FBGA88 [CX5005]  
M36L0R8060U3@FBGA56 [CX5099] M36L0R8060U3@FBGA80 [CX5052]  
M36L0R8060U3@FBGA88 [CX5005] M36L0T7040B0@FBGA88 [CX5005]  
M36L0T7040T0@FBGA88 [CX5005] M36L0T7050B0@FBGA88 [CX5005]  
M36L0T7050B1@FBGA88 [CX5005] M36L0T7050B2@FBGA88 [CX5005]  
M36L0T7050B3@FBGA80 [CX5052] M36L0T7050B3@FBGA88 [CX5005]  
M36L0T7050T0@FBGA88 [CX5005] M36L0T7050T1@FBGA88 [CX5005]  
M36L0T7050T2@FBGA88 [CX5005] M36L0T7050T3@FBGA80 [CX5052]  
M36L0T7050T3@FBGA88 [CX5005] M36L0T7060B0@FBGA88 [CX5005]  
M36L0T7060B1@FBGA88 [CX5005] M36L0T7060B2@FBGA88 [CX5005]  
M36L0T7060B3@FBGA88 [CX5005] M36L0T7060T0@FBGA88 [CX5005]  
M36L0T7060T1@FBGA88 [CX5005] M36L0T7060T2@FBGA88 [CX5005]  
M36L0T7060T3@FBGA88 [CX5005] M36L0T8050B0@FBGA88 [CX5005]  
M36L0T8050B1@FBGA88 [CX5005] M36L0T8050B3@FBGA88 [CX5005]  
M36L0T8050T0@FBGA88 [CX5005] M36L0T8050T1@FBGA88 [CX5005]  
M36L0T8050T3@FBGA88 [CX5005] M36L0T8060B0@FBGA88 [CX5005]  
M36L0T8060B1@FBGA88 [CX5005] M36L0T8060B3@FBGA80 [CX5052]  
M36L0T8060B3@FBGA88 [CX5005] M36L0T8060T0@FBGA88 [CX5005]  
M36L0T8060T1@FBGA88 [CX5005] M36L0T8060T3@FBGA80 [CX5052]  
M36L0T8060T3@FBGA88 [CX5005] M36P0R8060N0ZS@FBGA56 [CX5099]  
M36P0R8070N0ZS@FBGA56 [CX5099]  
M36W0R5020B0(EFP)@FBGA88 [CX5005]  
M36W0R5020B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5020T0(EFP)@FBGA88 [CX5005]  
M36W0R5020T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5030B0(EFP)@FBGA88 [CX5005]  
M36W0R5030B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5030T0(EFP)@FBGA88 [CX5005]  
M36W0R5030T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5030U5@TFBGA52 [CX5127] M36W0R5030U5@TFBGA88 [CX5005]  
M36W0R5040B0(EFP)@FBGA88 [CX5005]  
M36W0R5040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B1(EFP)@FBGA88 [CX5005]  
M36W0R5040B1(Q\_Word)@FBGA88 [CX5005]

M36W0R5040B2(EFP)@FBGA88 [CX5005]  
M36W0R5040B2(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B4(EFP)@FBGA88 [CX5005]  
M36W0R5040B4(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B5(EFP)@FBGA88 [CX5005]  
M36W0R5040B5(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B7(EFP)@FBGA88 [CX5005]  
M36W0R5040B7(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040L3@FBGA88 [CX5005] M36W0R5040L3@TFBGA56 [CX5127]  
M36W0R5040L4@TFBGA56 [CX5099] M36W0R5040L4@TFBGA88 [CX5005]  
M36W0R5040L6@TFBGA52 [CX5127] M36W0R5040L6@TFBGA88 [CX5005]  
M36W0R5040T0(EFP)@FBGA88 [CX5005]  
M36W0R5040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T1(EFP)@FBGA88 [CX5005]  
M36W0R5040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T2(EFP)@FBGA88 [CX5005]  
M36W0R5040T2(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T4(EFP)@FBGA88 [CX5005]  
M36W0R5040T4(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T5(EFP)@FBGA88 [CX5005]  
M36W0R5040T5(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T7(EFP)@FBGA88 [CX5005]  
M36W0R5040T7(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040U3@FBGA88 [CX5005] M36W0R5040U3@TFBGA56 [CX5127]  
M36W0R5040U4@TFBGA56 [CX5099] M36W0R5040U4@TFBGA88 [CX5005]  
M36W0R5040U5@TFBGA52 [CX5127] M36W0R5040U5@TFBGA88 [CX5005]  
M36W0R5040U6@TFBGA52 [CX5127] M36W0R5040U6@TFBGA88 [CX5005]  
M36W0R5050L6@TFBGA52 [CX5127] M36W0R5050L6@TFBGA88 [CX5005]  
M36W0R5050U6@TFBGA52 [CX5127] M36W0R5050U6@TFBGA88 [CX5005]  
M36W0R6030B0(EFP)@FBGA88 [CX5005]  
M36W0R6030B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6030T0(EFP)@FBGA88 [CX5005]  
M36W0R6030T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B0(EFP)@FBGA88 [CX5005]  
M36W0R6040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B1(EFP)@FBGA88 [CX5005]  
M36W0R6040B1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B3(EFP)@FBGA88 [CX5005]  
M36W0R6040B3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B4(EFP)@FBGA88 [CX5005]  
M36W0R6040B4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B7(EFP)@FBGA88 [CX5005]  
M36W0R6040B7(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040L3@FBGA88 [CX5005] M36W0R6040L4@TFBGA56 [CX5099]  
M36W0R6040L4@TFBGA56(ZTE) [CX5186]  
M36W0R6040L4@TFBGA88 [CX5005] M36W0R6040L6@TFBGA52 [CX5127]  
M36W0R6040L6@TFBGA88 [CX5005]  
M36W0R6040T0(EFP)@FBGA88 [CX5005]  
M36W0R6040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T1(EFP)@FBGA88 [CX5005]  
M36W0R6040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T3(EFP)@FBGA88 [CX5005]  
M36W0R6040T3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T4(EFP)@FBGA88 [CX5005]  
M36W0R6040T4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T7(EFP)@FBGA88 [CX5005]  
M36W0R6040T7(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040U3@FBGA88 [CX5005] M36W0R6040U4@TFBGA56 [CX5099]  
M36W0R6040U4@TFBGA56(ZTE) [CX5186]

M36W0R6040U4@TFBGA88 [CX5005] M36W0R6040U5@TFBGA52 [CX5127]  
M36W0R6040U5@TFBGA88 [CX5005] M36W0R6040U6@TFBGA52 [CX5127]  
M36W0R6040U6@TFBGA88 [CX5005]  
M36W0R6050B0(EFP)@FBGA88 [CX5005]  
M36W0R6050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050B1(EFP)@FBGA88 [CX5005]  
M36W0R6050B1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050B3(EFP)@FBGA88 [CX5005]  
M36W0R6050B3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050B4(EFP)@FBGA88 [CX5005]  
M36W0R6050B4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050L0@FBGA88 [CX5005] M36W0R6050L4@TFBGA56 [CX5099]  
M36W0R6050L4@TFBGA56(ZTE) [CX5186]  
M36W0R6050L4@TFBGA88 [CX5005] M36W0R6050L6@TFBGA52 [CX5127]  
M36W0R6050L6@TFBGA88 [CX5005]  
M36W0R6050T0(EFP)@FBGA88 [CX5005]  
M36W0R6050T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050T1(EFP)@FBGA88 [CX5005]  
M36W0R6050T1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050T3(EFP)@FBGA88 [CX5005]  
M36W0R6050T3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050T4(EFP)@FBGA88 [CX5005]  
M36W0R6050T4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050U0@FBGA88 [CX5005] M36W0R6050U4@TFBGA56 [CX5099]  
M36W0R6050U4@TFBGA56(ZTE) [CX5186]  
M36W0R6050U4@TFBGA88 [CX5005] M36W0R6050U5@TFBGA56 [CX5099]  
M36W0R6050U5@TFBGA88 [CX5005] M36W0R6050U6@TFBGA52 [CX5127]  
M36W0R6050U6@TFBGA88 [CX5005]  
M36W0R7050B0(EFP)@FBGA88 [CX5005]  
M36W0R7050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R7050T0(EFP)@FBGA88 [CX5005]  
M36W0R7050T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T5040B1(EFP)@FBGA88 [CX5005]  
M36W0T5040B1(Q\_Word)@FBGA88 [CX5005]  
M36W0T5040T1(EFP)@FBGA88 [CX5005]  
M36W0T5040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0T6030B0(EFP)@FBGA88 [CX5005]  
M36W0T6030B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6030T0(EFP)@FBGA88 [CX5005]  
M36W0T6030T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040B0(EFP)@FBGA88 [CX5005]  
M36W0T6040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040B1(EFP)@FBGA88 [CX5005]  
M36W0T6040B1(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040B3(EFP)@FBGA88 [CX5005]  
M36W0T6040B3(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040T0(EFP)@FBGA88 [CX5005]  
M36W0T6040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040T1(EFP)@FBGA88 [CX5005]  
M36W0T6040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040T3(EFP)@FBGA88 [CX5005]  
M36W0T6040T3(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050B0(EFP)@FBGA88 [CX5005]  
M36W0T6050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050B3(EFP)@FBGA88 [CX5005]  
M36W0T6050B3(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050T0(EFP)@FBGA88 [CX5005]  
M36W0T6050T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050T3(EFP)@FBGA88 [CX5005]

M36W0T6050T3(Q\_Word)@FBGA88 [CX5005]  
M36W0T7040B0(EFP)@FBGA88 [CX5005]  
M36W0T7040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T7040T0(EFP)@FBGA88 [CX5005]  
M36W0T7040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T7050B0(EFP)@FBGA88 [CX5005]  
M36W0T7050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T7050T0(EFP)@FBGA88 [CX5005]  
M36W0T7050T0(Q\_Word)@FBGA88 [CX5005]  
M45PE10@SO8N [CX1045#1] M45PE10@VFQPN8 [CX4005#1]  
M45PE16@SO8W [CX1044#1] M45PE16@VFQFPN8 [CX4005#1]  
M45PE20@SO8 [CX1045#1] M45PE20@VFQFPN8 [CX4005#1]  
M45PE40@SO8N [CX1045#1] M45PE40@SO8W [CX1044#1]  
M45PE40@VFQFPN8 [CX4005#1] M45PE80@QFN8L [CX4005#1]  
M45PE80@SO8N [CX1045#1] M45PE80@SO8W [CX1044#1]  
M45PE80@VFQFPN8 [CX4005#1] M58LR128KB@FBGA56 [CX5032]  
M58LR128KB@FBGA88 [CX5005] M58LR128KT@FBGA56 [CX5032]  
M58LR128KT@FBGA88 [CX5005] M58LR256KB@FBGA79 [CX5164]  
M58LR256KB@FBGA88 [CX5005] M58LR256KT@FBGA79 [CX5164]  
M58LR256KT@FBGA88 [CX5005] M58LT128KSB@FBGA64 [CX5004]  
M58LT128KST@FBGA64 [CX5004] M58LT256JSB@FBGA64 [CX5004]  
M58LT256JST@FBGA64 [CX5004] M58LT256KSB@FBGA64 [CX5004]  
M58LT256KST@FBGA64 [CX5004] M58WR016KB(EFP)@FBGA56 [CX5032]  
M58WR016KB(EFP)@FBGA88 [CX5005] M58WR016KB(Q\_Word)@FBGA56 [CX5032]  
M58WR016KB(Q\_Word)@FBGA88 [CX5005] M58WR016KT(EFP)@FBGA56 [CX5032]  
M58WR016KT(EFP)@FBGA88 [CX5005] M58WR016KT(Q\_Word)@FBGA56 [CX5032]  
M58WR016KT(Q\_Word)@FBGA88 [CX5005] M58WR032KB(EFP)@FBGA56 [CX5032]  
M58WR032KB(EFP)@FBGA88 [CX5005] M58WR032KB(Q\_Word)@FBGA56 [CX5032]  
M58WR032KB(Q\_Word)@FBGA88 [CX5005] M58WR032KT(EFP)@FBGA56 [CX5032]  
M58WR032KT(EFP)@FBGA88 [CX5005] M58WR032KT(Q\_Word)@FBGA56 [CX5032]  
M58WR032KT(Q\_Word)@FBGA88 [CX5005] M58WR064KB(EFP)@FBGA56 [CX5032]  
M58WR064KB(EFP)@FBGA88 [CX5005] M58WR064KB(Q\_Word)@FBGA56 [CX5032]  
M58WR064KB(Q\_Word)@FBGA88 [CX5005] M58WR064KT(EFP)@FBGA56 [CX5032]  
M58WR064KT(EFP)@FBGA88 [CX5005] M58WR064KT(Q\_Word)@FBGA56 [CX5032]  
M58WR064KT(Q\_Word)@FBGA88 [CX5005] M58WT032KB(EFP)@FBGA88 [CX5005]  
M58WT032KB(Q\_Word)@FBGA88 [CX5005] M58WT032KT(EFP)@FBGA88 [CX5005]  
M58WT032KT(Q\_Word)@FBGA88 [CX5005] M58WT064KB(EFP)@FBGA88 [CX5005]  
M58WT064KB(Q\_Word)@FBGA88 [CX5005] M58WT064KT(EFP)@FBGA88 [CX5005]  
M58WT064KT(Q\_Word)@FBGA88 [CX5005] N25Q032@BGA24 [CX5157]  
N25Q032@BGA24(fast mode) [CX5157]  
N25Q032@SOIC16 [CX1033#1]  
N25Q032@SOIC16(fast mode) [CX1033#1]  
N25Q032@SOIC8(150mil) [CX1045#1]  
N25Q032@SOIC8(150mil)(fast mode) [CX1045#1]  
N25Q032@SOIC8(208mil) [CX1044#1]  
N25Q032@SOIC8(208mil)(fast mode) [CX1044#1]  
N25Q032@VDFPN8(6\*5mm) [CX4005#1]  
N25Q032@VDFPN8(6\*5mm)(fast mode) [CX4005#1]



N25Q032@VDFPN8(8\*6mm) [CX4006#1]  
N25Q032@VDFPN8(8\*6mm)(fast mode) [CX4006#1]  
N25Q064@BGA24 [CX5157]  
N25Q064@BGA24(fast mode) [CX5157]  
N25Q064@SOIC16 [CX1033#1]  
N25Q064@SOIC16(fast mode) [CX1033#1]  
N25Q064@SOIC8(150mil) [CX1045#1]  
N25Q064@SOIC8(150mil)(fast mode) [CX1045#1]  
N25Q064@SOIC8(208mil) [CX1044#1]  
N25Q064@SOIC8(208mil)(fast mode) [CX1044#1]  
N25Q064@VDFPN8(6\*5mm) [CX4005#1]  
N25Q064@VDFPN8(6\*5mm)(fast mode) [CX4005#1]  
N25Q064@VDFPN8(8\*6mm) [CX4006#1]  
N25Q064@VDFPN8(8\*6mm)(fast mode) [CX4006#1]  
N25Q064A@BGA24 [CX5157] N25Q064A@SOIC16 [CX1033#1]  
N25Q064A@SOIC8(150mil) [CX1045#1]  
N25Q064A@SOIC8(208mil) [CX1044#1]  
N25Q064A@VDFPN8(6\*5mm) [CX4005#1]  
N25Q064A@VDFPN8(8\*6mm) [CX4006#1]  
N25Q128@BGA24 [CX5157] N25Q128@BGA24(JIUZHOU) [CX5157]  
N25Q128@SOIC16 [CX1033#1] N25Q128@VDFPN8 [CX4006#1]  
N25Q128A11B@BGA24 [CX5157] N25Q128A11B@SOIC16 [CX1033#1]  
N25Q128A11B@VDFPN8 [CX4006#1] N25Q128A11E@BGA24 [CX5157]  
N25Q128A11E@SOIC16 [CX1033#1] N25Q128A11E@VDFPN8 [CX4006#1]  
N25Q128A11T@BGA24 [CX5157] N25Q128A11T@SOIC16 [CX1033#1]  
N25Q128A11T@VDFPN8 [CX4006#1] N25Q128A13B@BGA24 [CX5157]  
N25Q128A13B@SOIC16 [CX1033#1] N25Q128A13B@VDFPN8 [CX4006#1]  
N25Q128A13E@BGA24 [CX5157] N25Q128A13E@SOIC16 [CX1033#1]  
N25Q128A13E@VDFPN8 [CX4006#1] N25Q128A13T@BGA24 [CX5157]  
N25Q128A13T@SOIC16 [CX1033#1] N25Q128A13T@VDFPN8 [CX4006#1]  
N25Q256A@BGA24 [CX5157] N25Q256A@SOIC16 [CX1033#1]  
N25Q256A@VDFN8 [CX4006#1] N25Q256A11E1240E [CX5157]  
N25Q256A11E1240F [CX5157] N25Q256A11EF840E [CX4006#1]  
N25Q256A11EF840F [CX4006#1] N25Q256A11ESF40F [CX1033#1]  
N25Q256A11ESF40G [CX1033#1] N25Q256A13E1240E [CX5157]  
N25Q256A13E1240F [CX5157] N25Q256A13EF840E [CX4006#1]  
N25Q256A13EF840F [CX4006#1] N25Q256A13ESF40F [CX1033#1]  
N25Q256A13ESF40G [CX1033#1] N25Q256A13Ex@BGA24 [CX5157]  
N25Q256A13Ex@SOIC16 [CX1033#1] N25Q256A13Ex@VDFN8 [CX4006#1]  
N3L0219071F5620@FBGA64 [CX5066] N3L0219081F5620@FBGA64 [CX5066]  
N3L0219091F5620@FBGA64 [CX5066] PC28F00AG18F@FBGA64 [CX5019]  
PC28F00AM29EWH@FBGA64 [CX5074] PC28F00AM29EWS@FBGA64 [CX5074]  
PC28F00AM29EWL@FBGA64 [CX5074] PC28F00AM29EWLS@FBGA64 [CX5074]  
PC28F00AP30BF@FBGA64 [CX5019] PC28F00AP30EF@FBGA64 [CX5019]  
PC28F00AP30TF@FBGA64 [CX5019] PC28F00AP33BF@FBGA64 [CX5019]  
PC28F00AP33EF@FBGA64 [CX5019] PC28F00AP33TF@FBGA64 [CX5019]  
PC28F00BM29EWH@FBGA64 [CX5074] PC28F00BP30EF@FBGA64 [CX5019]  
PC28F00BP33EF@FBGA64 [CX5019] PC28F064M29EWB@FBGA64 [CX5074]  
PC28F064M29EWH@FBGA64 [CX5074] PC28F064M29EWL@FBGA64 [CX5074]  
PC28F064M29EWT@FBGA64 [CX5074] PC28F128G18F@FBGA64 [CX5019]  
PC28F128J3F@FBGA64 [CX5004] PC28F128M29EWH@FBGA64 [CX5074]  
PC28F128M29EWL@FBGA64 [CX5074] PC28F128P30BF@FBGA64 [CX5004]  
PC28F128P30TF@FBGA64 [CX5004] PC28F128P33BF@FBGA64 [CX5019]  
PC28F128P33TF@FBGA64 [CX5019] PC28F256G18F@FBGA64 [CX5019]  
PC28F256J3F@FBGA64 [CX5004] PC28F256M29EWH@FBGA64 [CX5074]  
PC28F256M29EWS@FBGA64 [CX5074] PC28F256M29EWL@FBGA64 [CX5074]  
PC28F256M29EWLS@FBGA64 [CX5074] PC28F256P30BF@FBGA64 [CX5004]  
PC28F256P30TF@FBGA64 [CX5004] PC28F256P33BF@FBGA64 [CX5004]  
PC28F256P33TF@FBGA64 [CX5004] PC28F320J3F@FBGA64 [CX5004]

PC28F512G18F@FBGA64 [CX5019] PC28F512M29AWH@FBGA64 [CX5074]  
PC28F512M29AWL@FBGA64 [CX5074] PC28F512M29EWH@FBGA64 [CX5074]  
PC28F512M29EWS@FBGA64 [CX5074] PC28F512M29EWL@FBGA64 [CX5074]  
PC28F512M29EWS@FBGA64 [CX5074] PC28F512P30BF@FBGA64 [CX5019]  
PC28F512P30EF@FBGA64 [CX5019] PC28F512P30TF@FBGA64 [CX5019]  
PC28F512P33BF@FBGA64 [CX5019] PC28F512P33EF@FBGA64 [CX5019]  
PC28F512P33TF@FBGA64 [CX5019] PC28F640J3F@FBGA64 [CX5004]  
PC28F640P30BF@FBGA64 [CX5004] PC28F640P30TF@FBGA64 [CX5004]  
PC28F640P33BF@FBGA64 [CX5019] PC28F640P33TF@FBGA64 [CX5019]  
PC48F4400P0TB0E@FBGA64 [CX5004] PC48F4400P0VB0E@FBGA64 [CX5004]  
PF38F3040M0Y0QE@FBGA88 [CX5005] PF38F3040M0Y1QE@FBGA88 [CX5005]  
PF38F3040M0Y3DE@FBGA56 [CX5094] PF38F3040M0Y3DF@FBGA56 [CX5094]  
PF38F3040M0Y3DF@FBGA56(new) [CX5094] PF38F3050M0Y0QE@FBGA88 [CX5005]  
PF38F3050M0Y0QF@FBGA88 [CX5005] PF38F3050M0Y3DE@FBGA56 [CX5094]  
PF38F3050M0Y3DF@FBGA56 [CX5094] PF38F3050M0Y3DG@FBGA56 [CX5094]  
PF38F3050M0Y3DH@FBGA56 [CX5094] PF38F3050M0Y3QE@FBGA88 [CX5005]  
PF38F3050M0Y3QF@FBGA88 [CX5005] PF38F4050L0YAQE@FBGA88 [CX5005]  
PF38F4050L0YWQE@FBGA88 [CX5005] PF38F4050M0Y0Q0@FBGA88 [CX5005]  
PF38F4050M0Y1Q0@FBGA88 [CX5005] PF38F4050M0Y3DE@FBGA56 [CX5114]  
PF38F4050M0Y3DF@FBGA56 [CX5094] PF38F4050M0YEQ0@FBGA88 [CX5005]  
PF38F4050M0YEQF@FBGA88 [CX5005] PF38F4060M0Y3DE@FBGA56 [CX5114]  
PF38F4060M0Y3DF@FBGA56 [CX5114] PF38F4060M0Y3DG@FBGA56 [CX5114]  
PF38F4060M0Y3DH@FBGA56 [CX5114] PF38F5050L0Y3AE@FBGA64 [CX5066]  
PF38F5060L0Y3AE@FBGA64 [CX5066] PF38F5060M0Y3DE@FBGA56 [CX5134]  
PF38F5060M0Y3DF@FBGA56 [CX5114] PF38F5060M0Y3DG@FBGA56 [CX5114]  
PF38F5060M0Y3DH@FBGA56 [CX5114] PF38F5060M0Y3DJ@FBGA56 [CX5114]  
PF38F5060M0Y3DK@FBGA56 [CX5114] PF38F5066M0Y3DE@FBGA56 [CX5114]  
PF38F5070L0Y3AE@FBGA64 [CX5066] PF38F5070M0Y3DE@FBGA56 [CX5134]  
PF48F3000M0Y0QE@FBGA88 [CX5005] PF48F3000P0ZBQE@FBGA88 [CX5005]  
PF48F3000P0ZTQE@FBGA88 [CX5005] PF48F4000P0ZBQE@FBGA88 [CX5001]  
PF48F4000P0ZTQE@FBGA88 [CX5001] PF48F4400P0VBQE@FBGA88 [CX5001]  
PZ28F032M29EWB@FBGA48 [CX5002] PZ28F032M29EWH@FBGA48 [CX5002]  
PZ28F032M29EWL@FBGA48 [CX5002] PZ28F032M29EWT@FBGA48 [CX5002]  
PZ28F064M29EWB@FBGA48 [CX5002] PZ28F064M29EWH@FBGA48 [CX5002]  
PZ28F064M29EWL@FBGA48 [CX5002] PZ28F064M29EWT@FBGA48 [CX5002]  
RC28F00BM29EWH@FBGA64 [CX5074] RC28F128J3F@FBGA64 [CX5004]  
RC28F128M29EWH@FBGA64 [CX5074] RC28F128M29EWL@FBGA64 [CX5074]  
RC28F128P30BF@FBGA64 [CX5004] RC28F128P30TF@FBGA64 [CX5004]  
RC28F128P33BF@FBGA64 [CX5019] RC28F128P33TF@FBGA64 [CX5019]  
RC28F256J3F@FBGA64 [CX5004] RC28F256M29EWH@FBGA64 [CX5074]  
RC28F256M29EWS@FBGA64 [CX5074] RC28F256M29EWL@FBGA64 [CX5074]  
RC28F256M29EWS@FBGA64 [CX5074] RC28F256P30BF@FBGA64 [CX5004]  
RC28F256P30TF@FBGA64 [CX5004] RC28F256P33BF@FBGA64 [CX5004]  
RC28F256P33TF@FBGA64 [CX5004] RC28F320J3F@FBGA64 [CX5004]  
RC28F512M29EWH@FBGA64 [CX5074] RC28F512M29EWS@FBGA64 [CX5074]  
RC28F512M29EWL@FBGA64 [CX5074] RC28F512M29EWS@FBGA64 [CX5074]  
RC28F640J3F@FBGA64 [CX5004] RC28F640P30BF@FBGA64 [CX5004]  
RC28F640P30TF@FBGA64 [CX5004] RC28F640P33BF@FBGA64 [CX5019]  
RC28F640P33TF@FBGA64 [CX5019] RC48F4400P0TB0E@FBGA64 [CX5004]  
RC48F4400P0VB0E@FBGA64 [CX5004] RD38F5070L0Y3AE@FBGA64 [CX5127]  
RD48F3000P0ZBQE@FBGA88 [CX5005] RD48F3000P0ZTQE@FBGA88 [CX5005]  
RD48F4400L0ZDN0@FBGA88 [CX5001] RD48F4440LVYBQ0@FBGA88 [CX5001]  
RD48F4444LLZBB0@FBGA103 [CX50UN] RD48F4444LVYBB0@FBGA103 [CX50UN]  
RF48F4400P0VBQE@FBGA88 [CX5001] TE28F128J3F@TSOP56 [CX1011]  
TE28F128P30BF@TSOP56 [CX1011] TE28F128P30TF@TSOP56 [CX1011]  
TE28F128P33BF@TSOP56 [CX1011] TE28F128P33TF@TSOP56 [CX1011]  
TE28F256J3F@TSOP56 [CX1011] TE28F256P30BF@TSOP56 [CX1011]  
TE28F256P30TF@TSOP56 [CX1011] TE28F256P33BF@TSOP56 [CX1011]

TE28F256P33TF@TSOP56 [CX1011]  
TE28F640J3F@TSOP56 [CX1011]

TE28F320J3F@TSOP56 [CX1011]

## NUVOTON

### MICROCONTROLLER

M0516LAN@QFP48 [CX3007]  
M0516ZAN@QFN32 [CX4015]  
M052LAN@QFP48 [CX3007]  
M052ZAN@QFN32 [CX4015]  
M054LAN@QFP48 [CX3007]  
M054ZAN@QFN32 [CX4015]  
M058LAN@QFP48 [CX3007]  
M058ZAN@QFN32 [CX4015]  
MINI51LAN@QFN33 [CX4015]  
MINI52LAN@QFN33 [CX4015]  
MINI54LAN@QFN33 [CX4015]  
N78E055ADG [CX0001]  
N78E055ALG@TQFP48 [CX3007]  
N78E059ADG [CX0001]  
N78E059ALG@TQFP48 [CX3007]  
N78E366ADG [CX0001]  
N78E366ALG@LQFP48 [CX3007]  
N78E517ADG [CX0001]  
N78E517ALG@LQFP48 [CX3007]  
N79E234ALG@TQFP48 [CX3007]  
N79E235ALG@TQFP48 [CX3007]  
N79E342AKG [CX0001]  
N79E342RAKG [CX0001]  
N79E352AEG [CX0001]  
N79E352ALG@TQFP48 [CX3007]  
N79E813A [CX0001]  
N79E813A@SOIC28 [CX1033]  
N79E813A@TSSOP28 [CX1001]  
N79E814A@SOIC20 [CX1033]  
N79E814A@TSSOP20 [CX1000]  
N79E815A [CX0001]  
N79E815A@SOIC28 [CX1033]  
N79E815A@TSSOP28 [CX1001]  
N79E8213ASG@SOP20 [CX1033]  
N79E8213RASG@SOP20 [CX1033]  
N79E822A@SOP20 [CX1033]  
N79E823A@SOP20 [CX1033]  
N79E824A@SOP20 [CX1033]  
N79E825A@SOP20 [CX1033]  
N79E843A@SOIC20 [CX1033]  
N79E844A [CX0001]  
N79E844A@TSSOP20 [CX1000]  
N79E845A@SOIC20 [CX1033]  
N79E853A@SOIC28 [CX1033]  
N79E854A@SOIC28 [CX1033]  
N79E855A@SOIC28 [CX1033]  
N79E875ALG@TQFP48 [CX3007]  
NUC100LC1AN@LQFP48 [CX3007]  
NUC100LC1CN@LQFP48 [CX3007]  
NUC100LD1AN@LQFP48 [CX3007]  
NUC100LD1CN@LQFP48 [CX3007]

M0516LBN@QFP48 [CX3007]  
M0516ZBN@QFN32 [CX4015]  
M052LBN@QFP48 [CX3007]  
M052ZBN@QFN32 [CX4015]  
M054LBN@QFP48 [CX3007]  
M054ZBN@QFN32 [CX4015]  
M058LBN@QFP48 [CX3007]  
M058ZBN@QFN32 [CX4015]  
MINI51LAN@QFP48 [CX3007]  
MINI52LAN@QFP48 [CX3007]  
MINI54LAN@QFP48 [CX3007]  
N78E055AFG@TQFP44 [CX3002]  
N78E055APG@PLCC44 [CX2044]  
N78E059AFG@TQFP44 [CX3002]  
N78E059APG@PLCC44 [CX2044]  
N78E366AFG@PQFP44 [CX3002]  
N78E366APG@PLCC44 [CX2044]  
N78E517AFG@PQFP44 [CX3002]  
N78E517APG@PLCC44 [CX2044]  
N79E234RALG@TQFP48 [CX3007]  
N79E235RALG@TQFP48 [CX3007]  
N79E342ASG@SOP16 [CX1033]  
N79E342RASG@SOP16 [CX1033]  
N79E352AFG@TQFP44 [CX3002]  
N79E352APG@PLCC44 [CX2044]  
N79E813A@SOIC20 [CX1033]  
N79E813A@TSSOP20 [CX1000]  
N79E814A [CX0001]  
N79E814A@SOIC28 [CX1033]  
N79E814A@TSSOP28 [CX1001]  
N79E815A@SOIC20 [CX1033]  
N79E815A@TSSOP20 [CX1000]  
N79E8213AKG [CX0001]  
N79E8213RAKG [CX0001]  
N79E822A [CX0001]  
N79E823A [CX0001]  
N79E824A [CX0001]  
N79E825A [CX0001]  
N79E843A [CX0001]  
N79E843A@TSSOP20 [CX1000]  
N79E844A@SOIC20 [CX1033]  
N79E845A [CX0001]  
N79E845A@TSSOP20 [CX1000]  
N79E853A@TSSOP28 [CX1000]  
N79E854A@TSSOP28 [CX1000]  
N79E855A@TSSOP28 [CX1000]  
N79E875RALG@TQFP48 [CX3007]  
NUC100LC1BN@LQFP48 [CX3007]  
NUC100LC1DN@LQFP48 [CX3007]  
NUC100LD1BN@LQFP48 [CX3007]  
NUC100LD1DN@LQFP48 [CX3007]

NUC100LD2AN@LQFP48 [CX3007] NUC100LD2BN@LQFP48 [CX3007]  
NUC100LD2CN@LQFP48 [CX3007] NUC100LD2DN@LQFP48 [CX3007]  
NUC100LD3AN@LQFP48 [CX3007] NUC100LD3CN@LQFP48 [CX3007]  
NUC100LD3DN@LQFP48 [CX3007] NUC100LE3AN@LQFP48 [CX3007]  
NUC100LE3CN@LQFP48 [CX3007] NUC100LE3DN@LQFP48 [CX3007]  
NUC100RC1AN@LQFP64 [CX3011] NUC100RC1BN@LQFP64 [CX3011]  
NUC100RC1CN@LQFP64 [CX3011] NUC100RC1DN@LQFP64 [CX3011]  
NUC100RD1AN@LQFP64 [CX3011] NUC100RD1BN@LQFP64 [CX3011]  
NUC100RD1CN@LQFP64 [CX3011] NUC100RD1DN@LQFP64 [CX3011]  
NUC100RD2AN@LQFP64 [CX3011] NUC100RD2BN@LQFP64 [CX3011]  
NUC100RD2CN@LQFP64 [CX3011] NUC100RD2DN@LQFP64 [CX3011]  
NUC100RD3AN@LQFP64 [CX3011] NUC100RD3CN@LQFP64 [CX3011]  
NUC100RD3DN@LQFP64 [CX3011] NUC100RE3AN@LQFP64 [CX3011]  
NUC100RE3CN@LQFP64 [CX3011] NUC100RE3DN@LQFP64 [CX3011]  
NUC100VD2AN@LQFP100 [CX3021] NUC100VD2CN@LQFP100 [CX3021]  
NUC100VD2DN@LQFP100 [CX3021] NUC100VD3AN@LQFP100 [CX3021]  
NUC100VD3CN@LQFP100 [CX3021] NUC100VD3DN@LQFP100 [CX3021]  
NUC100VE3AN@LQFP100 [CX3021] NUC100VE3CN@LQFP100 [CX3021]  
NUC100VE3DN@LQFP100 [CX3021] NUC102LC1AN@QFP48 [CX3007]  
NUC102LD2AN@QFP48 [CX3007] NUC102YC1AN@QFN36 [CX4029]  
NUC102YD2AN@QFN36 [CX4029] NUC102ZC1AN@QFN33 [CX4015]  
NUC102ZC2AN@QFN33 [CX4015] NUC102ZD2AN@QFN33 [CX4015]  
NUC120LC1AN@LQFP48 [CX3007] NUC120LC1BN@LQFP48 [CX3007]  
NUC120LC1CN@LQFP48 [CX3007] NUC120LC1DN@LQFP48 [CX3007]  
NUC120LD1AN@LQFP48 [CX3007] NUC120LD1BN@LQFP48 [CX3007]  
NUC120LD1CN@LQFP48 [CX3007] NUC120LD1DN@LQFP48 [CX3007]  
NUC120LD2AN@LQFP48 [CX3007] NUC120LD2BN@LQFP48 [CX3007]  
NUC120LD2CN@LQFP48 [CX3007] NUC120LD2DN@LQFP48 [CX3007]  
NUC120LD3AN@LQFP48 [CX3007] NUC120LD3CN@LQFP48 [CX3007]  
NUC120LD3DN@LQFP48 [CX3007] NUC120LE3AN@LQFP48 [CX3007]  
NUC120LE3CN@LQFP48 [CX3007] NUC120LE3DN@LQFP48 [CX3007]  
NUC120RC1AN@LQFP64 [CX3011] NUC120RC1BN@LQFP64 [CX3011]  
NUC120RC1CN@LQFP64 [CX3011] NUC120RC1DN@LQFP64 [CX3011]  
NUC120RD1AN@LQFP64 [CX3011] NUC120RD1BN@LQFP64 [CX3011]  
NUC120RD1CN@LQFP64 [CX3011] NUC120RD1DN@LQFP64 [CX3011]  
NUC120RD2AN@LQFP64 [CX3011] NUC120RD2BN@LQFP64 [CX3011]  
NUC120RD2CN@LQFP64 [CX3011] NUC120RD2DN@LQFP64 [CX3011]  
NUC120RD3AN@LQFP64 [CX3011] NUC120RD3CN@LQFP64 [CX3011]  
NUC120RD3DN@LQFP64 [CX3011] NUC120RE3AN@LQFP64 [CX3011]  
NUC120RE3CN@LQFP64 [CX3011] NUC120RE3DN@LQFP64 [CX3011]  
NUC120VD2AN@LQFP100 [CX3021] NUC120VD2CN@LQFP100 [CX3021]  
NUC120VD2DN@LQFP100 [CX3021] NUC120VD3AN@LQFP100 [CX3021]  
NUC120VD3CN@LQFP100 [CX3021] NUC120VD3DN@LQFP100 [CX3021]  
NUC120VE3AN@LQFP100 [CX3021] NUC120VE3CN@LQFP100 [CX3021]  
NUC120VE3DN@LQFP100 [CX3021] NUC122LC1AN@QFP48 [CX3007]  
NUC122LD2AN@QFP48 [CX3007] NUC122SC1AN@QFP64 [CX3085]  
NUC122SD2AN@QFP64 [CX3085] NUC122SD2AN@QFP64(HW) [CX3085]  
NUC122ZC1AN@QFN33 [CX4015] NUC122ZD2AN@QFN33 [CX4015]  
NUC130LC1CN@LQFP48 [CX3007] NUC130LD2AN@LQFP48 [CX3007]  
NUC130LD2CN@LQFP48 [CX3007] NUC130LD3AN@LQFP48 [CX3007]  
NUC130LE3AN@LQFP48 [CX3007] NUC130LE3CN@LQFP48 [CX3007]  
NUC130RC1CN@LQFP64 [CX3011] NUC130RD2AN@LQFP64 [CX3011]  
NUC130RD2CN@LQFP64 [CX3011] NUC130RD3AN@LQFP64 [CX3011]  
NUC130RE3AN@LQFP64 [CX3011] NUC130RE3CN@LQFP64 [CX3011]  
NUC130VD2AN@LQFP100 [CX3021] NUC130VD3AN@LQFP100 [CX3021]  
NUC130VE3AN@LQFP100 [CX3021] NUC130VE3CN@LQFP100 [CX3021]  
NUC140LC1CN@LQFP48 [CX3007] NUC140LD2AN@LQFP48 [CX3007]  
NUC140LD2CN@LQFP48 [CX3007] NUC140LD3AN@LQFP48 [CX3007]  
NUC140LE3AN@LQFP48 [CX3007] NUC140LE3CN@LQFP48 [CX3007]

NUC140RC1CN@LQFP64 [CX3011]  
NUC140RD2CN@LQFP64 [CX3011]  
NUC140RE3AN@LQFP64 [CX3011]  
NUC140VD2AN@LQFP100 [CX3021]  
NUC140VE3AN@LQFP100 [CX3021]  
NUC200LC2AN@LQFP48 [CX3007]  
NUC200LE3AN@LQFP48 [CX3007]  
NUC200SD2AN@LQFP64 [CX3011]  
NUC200VE3AN@LQFP100 [CX3021]  
NUC220LD2AN@LQFP48 [CX3007]  
NUC220SC2AN@LQFP64 [CX3011]  
NUC220SE3AN@LQFP64 [CX3011]  
W77E058A [CX0001]  
W77E058A@TQFP44 [CX3002]  
W77E516@PLCC44 [CX2044]  
W77E532 [CX0001]  
W77E532@TQFP44 [CX3002]  
W77E532A@PLCC44 [CX2044]  
W77E58 [CX0001]  
W77E58@TQFP44 [CX3002]  
W77IE58@PLCC44 [CX2044]  
W77L058A [CX0001]  
W77L058A@TQFP44 [CX3002]  
W77L516A@PLCC44 [CX2044]  
W77L532A [CX0001]  
W77L532A@TQFP44 [CX3002]  
W77LE516@PLCC44 [CX2044]  
W77LE532 [CX0001]  
W77LE532@TQFP44 [CX3002]  
W77LE58@PLCC44 [CX2044]  
W77LE58A [CX0001]  
W77LE58A@TQFP44 [CX3002]  
W78E051B@PLCC44 [CX2044]  
W78E051C [CX0001]  
W78E051C@TQFP44 [CX3002]  
W78E051DFG@PQFP44 [CX3002]  
W78E051DPG@PLCC44 [CX2044]  
W78E052B@PLCC44 [CX2044]  
W78E052C [CX0001]  
W78E052C@TQFP44 [CX3002]  
W78E052DFG@PQFP44 [CX3002]  
W78E052DPG@PLCC44 [CX2044]  
W78E054B@PLCC44 [CX2044]  
W78E054C [CX0001]  
W78E054C@TQFP44 [CX3002]  
W78E054DFG@PQFP44 [CX3002]  
W78E054DPG@PLCC44 [CX2044]  
W78E058B@PLCC44 [CX2044]  
W78E058DDG [CX0001]  
W78E058DLG@TQFP48 [CX3007]  
W78E065 [CX0001]  
W78E065@TQFP44 [CX3002]  
W78E354(dip48) [CX0001]  
W78E365 [CX0001]  
W78E365@TQFP44 [CX3002]  
W78E365A@PLCC44 [CX2044]  
W78E374B [CX0001]  
W78E378E [CX0001]  
W78E51 [CX0001]

NUC140RD2AN@LQFP64 [CX3011]  
NUC140RD3AN@LQFP64 [CX3011]  
NUC140RE3CN@LQFP64 [CX3011]  
NUC140VD3AN@LQFP100 [CX3021]  
NUC140VE3CN@LQFP100 [CX3021]  
NUC200LD2AN@LQFP48 [CX3007]  
NUC200SC2AN@LQFP64 [CX3011]  
NUC200SE3AN@LQFP64 [CX3011]  
NUC220LC2AN@LQFP48 [CX3007]  
NUC220LE3AN@LQFP48 [CX3007]  
NUC220SD2AN@LQFP64 [CX3011]  
NUC220VE3AN@LQFP100 [CX3021]  
W77E058A@PLCC44 [CX2044]  
W77E516 [CX0001]  
W77E516@TQFP44 [CX3002]  
W77E532@PLCC44 [CX2044]  
W77E532A [CX0001]  
W77E532A@TQFP44 [CX3002]  
W77E58@PLCC44 [CX2044]  
W77IE58 [CX0001]  
W77IE58@TQFP44 [CX3002]  
W77L058A@PLCC44 [CX2044]  
W77L516A [CX0001]  
W77L516A@TQFP44 [CX3002]  
W77L532A@PLCC44 [CX2044]  
W77LE516 [CX0001]  
W77LE516@TQFP44 [CX3002]  
W77LE532@PLCC44 [CX2044]  
W77LE58 [CX0001]  
W77LE58@TQFP44 [CX3002]  
W77LE58A@PLCC44 [CX2044]  
W78E051B [CX0001]  
W78E051B@TQFP44 [CX3002]  
W78E051C@PLCC44 [CX2044]  
W78E051DDG [CX0001]  
W78E051DLG@LQFP48 [CX3007]  
W78E052B [CX0001]  
W78E052B@TQFP44 [CX3002]  
W78E052C@PLCC44 [CX2044]  
W78E052DDG [CX0001]  
W78E052DLG@LQFP48 [CX3007]  
W78E054B [CX0001]  
W78E054B@TQFP44 [CX3002]  
W78E054C@PLCC44 [CX2044]  
W78E054DDG [CX0001]  
W78E054DLG@LQFP48 [CX3007]  
W78E058B [CX0001]  
W78E058B@TQFP44 [CX3002]  
W78E058DFG@TQFP44 [CX3002]  
W78E058DPG@PLCC44 [CX2044]  
W78E065@PLCC44 [CX2044]  
W78E354(dip40) [CX0001]  
W78E354@PLCC68 [CX2068]  
W78E365@PLCC44 [CX2044]  
W78E365A [CX0001]  
W78E365A@TQFP44 [CX3002]  
W78E378 [CX0001]  
W78E378P@PLCC44 [CX2044]  
W78E51@PLCC44 [CX2044]

W78E51@TQFP44 [CX3002]  
W78E516@PLCC44 [CX2044]  
W78E516B [CX0001]  
W78E516B@TQFP44 [CX3002]  
W78E516DFG@TQFP44 [CX3002]  
W78E516DPG@PLCC44 [CX2044]  
W78E51B@PLCC44 [CX2044]  
W78E51B@TQFP44 [CX3003]  
W78E51C@PLCC44 [CX2044]  
W78E52 [CX0001]  
W78E52@TQFP44 [CX3002]  
W78E52B@PLCC44 [CX2044]  
W78E52C [CX0001]  
W78E52C@TQFP44 [CX3002]  
W78E54@PLCC44 [CX2044]  
W78E54@TQFP44 [CX3003]  
W78E54B@PLCC44 [CX2044]  
W78E54C [CX0001]  
W78E54C@TQFP44 [CX3002]  
W78E58@PLCC44 [CX2044]  
W78E58@TQFP44 [CX3003]  
W78E58B@PLCC44 [CX2044]  
W78E62B [CX0001]  
W78E62B@TQFP44 [CX3002]  
W78E65@PLCC44 [CX2044]  
W78E858 [CX0001]  
W78E858@TQFP44 [CX3002]  
W78ERD2@PLCC44 [CX2044]  
W78I051DDG [CX0001]  
W78I051DLG@LQFP48 [CX3007]  
W78I052 [CX0001]  
W78I052DDG [CX0001]  
W78I052DLG@LQFP48 [CX3007]  
W78I054 [CX0001]  
W78I054DDG [CX0001]  
W78I054DLG@LQFP48 [CX3007]  
W78IE52 [CX0001]  
W78IE54 [CX0001]  
W78IRD2 [CX0001]  
W78IRD2@TQFP44 [CX3002]  
W78L051A@PLCC44 [CX2044]  
W78L051C [CX0001]  
W78L051C@TQFP44 [CX3002]  
W78L052A@PLCC44 [CX2044]  
W78L052C [CX0001]  
W78L052C@TQFP44 [CX3002]  
W78L054A@PLCC44 [CX2044]  
W78L054C [CX0001]  
W78L054C@TQFP44 [CX3002]  
W78L058A@PLCC44 [CX2044]  
W78L365 [CX0001]  
W78L365@TQFP44 [CX3002]  
W78L365A [CX0001]  
W78L365A@TQFP44 [CX3002]  
W78L516 [CX0001]  
W78L516@TQFP44 [CX3002]  
W78L516A@PLCC44 [CX2044]  
W78L812A [CX0001]  
W78L812A@TQFP44 [CX3002]

W78E516 [CX0001]  
W78E516@TQFP44 [CX3002]  
W78E516B@PLCC44 [CX2044]  
W78E516DDG [CX0001]  
W78E516DLG@TQFP48 [CX3007]  
W78E51B [CX0001]  
W78E51B@PQFP44 [CX3002]  
W78E51C [CX0001]  
W78E51C@TQFP44 [CX3002]  
W78E52@PLCC44 [CX2044]  
W78E52B [CX0001]  
W78E52B@TQFP44 [CX3002]  
W78E52C@PLCC44 [CX2044]  
W78E54 [CX0001]  
W78E54@PQFP44 [CX3002]  
W78E54B [CX0001]  
W78E54B@TQFP44 [CX3002]  
W78E54C@PLCC44 [CX2044]  
W78E58 [CX0001]  
W78E58@PQFP44 [CX3002]  
W78E58B [CX0001]  
W78E58B@TQFP44 [CX3002]  
W78E62B@PLCC44 [CX2044]  
W78E65 [CX0001]  
W78E65@TQFP44 [CX3002]  
W78E858@PLCC44 [CX2044]  
W78ERD2 [CX0001]  
W78ERD2@TQFP44 [CX3002]  
W78I051DFG@PQFP44 [CX3002]  
W78I051DPG@PLCC44 [CX2044]  
W78I052@PLCC44 [CX2044]  
W78I052DFG@PQFP44 [CX3002]  
W78I052DPG@PLCC44 [CX2044]  
W78I054@PLCC44 [CX2044]  
W78I054DFG@PQFP44 [CX3002]  
W78I054DPG@PLCC44 [CX2044]  
W78IE52@PLCC44 [CX2044]  
W78IE54@PLCC44 [CX2044]  
W78IRD2@PLCC44 [CX2044]  
W78L051A [CX0001]  
W78L051A@TQFP44 [CX3002]  
W78L051C@PLCC44 [CX2044]  
W78L052A [CX0001]  
W78L052A@TQFP44 [CX3002]  
W78L052C@PLCC44 [CX2044]  
W78L054A [CX0001]  
W78L054A@TQFP44 [CX3002]  
W78L054C@PLCC44 [CX2044]  
W78L058A [CX0001]  
W78L058A@TQFP44 [CX3002]  
W78L365@PLCC44 [CX2044]  
W78L365@TQFP48 [CX3007]  
W78L365A@PLCC44 [CX2044]  
W78L365A@TQFP48 [CX3007]  
W78L516@PLCC44 [CX2044]  
W78L516A [CX0001]  
W78L516A@TQFP44 [CX3002]  
W78L812A@PLCC44 [CX2044]  
W78LE365 [CX0001]

W78LE365@PLCC44 [CX2044]  
W78LE365@TQFP48 [CX3007]  
W78LE51@PLCC44 [CX2044]  
W78LE516 [CX0001]  
W78LE516@TQFP44 [CX3002]  
W78LE51C@PLCC44 [CX2044]  
W78LE52 [CX0001]  
W78LE52@TQFP44 [CX3002]  
W78LE52C@PLCC44 [CX2044]  
W78LE54 [CX0001]  
W78LE54@TQFP44 [CX3002]  
W78LE54C@PLCC44 [CX2044]  
W78LE58 [CX0001]  
W78LE58@TQFP44 [CX3002]  
W78LE812@PLCC44 [CX2044]  
W79E201@PLCC44 [CX2044]  
W79E2051(dip14) [CX0001]  
W79E2051(dip20) [CX0001]  
W79E2051@SOIC16 [CX1033]  
W79E2051R(dip20) [CX0001]  
W79E225ALG@TQFP48 [CX3007]  
W79E226ALG@TQFP48 [CX3007]  
W79E227ALG@TQFP48 [CX3007]  
W79E4051(dip14) [CX0001]  
W79E4051(dip20) [CX0001]  
W79E4051@SOIC16 [CX1033]  
W79E4051R(dip20) [CX0001]  
W79E532 [CX0001]  
W79E532@TQFP44 [CX3002]  
W79E532A@PLCC44 [CX2044]  
W79E533A@PLCC44 [CX2044]  
W79E632@PLCC44 [CX2044]  
W79E632A [CX0001]  
W79E632A@TQFP44 [CX3002]  
W79E801A [CX0001]  
W79E802A [CX0001]  
W79E803A [CX0001]  
W79E804A [CX0001]  
W79E821A [CX0001]  
W79E822A [CX0001]  
W79E822B [CX0001]  
W79E823A [CX0001]  
W79E823B [CX0001]  
W79E824A [CX0001]  
W79E825A [CX0001]  
W79E831A [CX0001]  
W79E832A [CX0001]  
W79E833A [CX0001]  
W79E834A [CX0001]  
W79L532 [CX0001]  
W79L532@TQFP44 [CX3002]  
W79L632@PLCC44 [CX2044]  
W79L632A [CX0001]  
W79L632A@TQFP44 [CX3002]  
W99100DG@TQFP48 [CX3007]

W78LE365@TQFP44 [CX3002]  
W78LE51 [CX0001]  
W78LE51@TQFP44 [CX3002]  
W78LE516@PLCC44 [CX2044]  
W78LE51C [CX0001]  
W78LE51C@TQFP44 [CX3002]  
W78LE52@PLCC44 [CX2044]  
W78LE52C [CX0001]  
W78LE52C@TQFP44 [CX3002]  
W78LE54@PLCC44 [CX2044]  
W78LE54C [CX0001]  
W78LE54C@TQFP44 [CX3002]  
W78LE58@PLCC44 [CX2044]  
W78LE812 [CX0001]  
W78LE812@TQFP44 [CX3002]  
W79E201@TQFP44 [CX3002]  
W79E2051(dip16) [CX0001]  
W79E2051@SOIC14 [CX1033]  
W79E2051@SOIC20 [CX1033]  
W79E2051R@SOIC20 [CX1033]  
W79E225APG@PLCC44 [CX2044]  
W79E226APG@PLCC44 [CX2044]  
W79E227APG@PLCC44 [CX2044]  
W79E4051(dip16) [CX0001]  
W79E4051@SOIC14 [CX1033]  
W79E4051@SOIC20 [CX1033]  
W79E4051R@SOIC20 [CX1033]  
W79E532@PLCC44 [CX2044]  
W79E532A [CX0001]  
W79E532A@TQFP44 [CX3002]  
W79E632 [CX0001]  
W79E632@TQFP44 [CX3002]  
W79E632A@PLCC44 [CX2044]  
W79E633A@PLCC44 [CX2044]  
W79E801A@SOIC20 [CX1033]  
W79E802A@SOIC20 [CX1033]  
W79E803A@SOIC20 [CX1033]  
W79E804A@SOIC20 [CX1033]  
W79E821A@SOIC20 [CX1033]  
W79E822A@SOIC20 [CX1033]  
W79E822B@SOIC20 [CX1033]  
W79E823A@SOIC20 [CX1033]  
W79E823B@SOIC20 [CX1033]  
W79E824A@SOIC20 [CX1033]  
W79E825A@SOIC20 [CX1033]  
W79E831A@SOIC28 [CX1033]  
W79E832A@SOIC28 [CX1033]  
W79E833A@SOIC28 [CX1033]  
W79E834A@SOIC28 [CX1033]  
W79L532@PLCC44 [CX2044]  
W79L632 [CX0001]  
W79L632@TQFP44 [CX3002]  
W79L632A@PLCC44 [CX2044]  
W79L633A@PLCC44 [CX2044]

## MICROCONTROLLER

EM773@QFN33 [CX4016]  
LPC1110FDH20 [CX1027]  
LPC1111/101@QFN33 [CX4016]  
LPC1111/102@LQFP48 [CX3007]  
LPC1111/102@QFP44 [CX3005]  
LPC1111/103@QFN33 [CX4016]  
LPC1111/201@LQFP48 [CX3007]  
LPC1111/201@QFP44 [CX3005]  
LPC1111/202@QFN33 [CX4016]  
LPC1111/203@LQFP48 [CX3007]  
LPC1111/203@QFP44 [CX3005]  
LPC1111@QFN33 [CX4016]  
LPC1111FD20 [CX1033]  
LPC1112/101@LQFP48 [CX3007]  
LPC1112/101@QFP44 [CX3005]  
LPC1112/102@QFN33 [CX4016]  
LPC1112/103@LQFP48 [CX3007]  
LPC1112/103@QFP44 [CX3005]  
LPC1112/201@QFN33 [CX4016]  
LPC1112/202@LQFP48 [CX3007]  
LPC1112/202@QFP44 [CX3005]  
LPC1112/203@QFN33 [CX4016]  
LPC1112@LQFP48 [CX3007]  
LPC1112@QFP44 [CX3005]  
LPC1112FDH20 [CX1033]  
LPC1113/101@QFN33 [CX4016]  
LPC1113/102@LQFP48 [CX3007]  
LPC1113/102@QFP44 [CX3005]  
LPC1113/103@QFN33 [CX4016]  
LPC1113/201@LQFP48 [CX3007]  
LPC1113/201@QFP44 [CX3005]  
LPC1113/202@QFN33 [CX4016]  
LPC1113/203@LQFP48 [CX3007]  
LPC1113/203@QFP44 [CX3005]  
LPC1113/301@QFP44 [CX3005]  
LPC1113/302@QFN33 [CX4016]  
LPC1113/302@QFP48 [CX3007]  
LPC1113/303@QFP44 [CX3005]  
LPC1113@LQFP48 [CX3007]  
LPC1113@QFP44 [CX3005]  
LPC1113FDH20 [CX1033]  
LPC1114/101@QFN33 [CX4016]  
LPC1114/102@LQFP48 [CX3007]  
LPC1114/102@QFP44 [CX3005]  
LPC1114/103@QFN33 [CX4016]  
LPC1114/201@LQFP48 [CX3007]  
LPC1114/201@QFP44 [CX3005]  
LPC1114/202@QFN33 [CX4016]  
LPC1114/203@LQFP48 [CX3007]  
LPC1114/203@QFP44 [CX3005]  
LPC1114/301@QFP44 [CX3005]  
LPC1114/302@QFN33 [CX4016]  
LPC1114/302@QFP48 [CX3007]  
LPC1114/303@QFP44 [CX3005]  
LPC1114/323@QFN33 [CX4016]  
LPC1114/323@QFP48 [CX3007]  
LPC1114/333@QFP44 [CX3005]  
LPC1114@LQFP48 [CX3007]  
LPC1110FD20 [CX1033]  
LPC1111/101@LQFP48 [CX3007]  
LPC1111/101@QFP44 [CX3005]  
LPC1111/102@QFN33 [CX4016]  
LPC1111/103@LQFP48 [CX3007]  
LPC1111/103@QFP44 [CX3005]  
LPC1111/201@QFN33 [CX4016]  
LPC1111/202@LQFP48 [CX3007]  
LPC1111/202@QFP44 [CX3005]  
LPC1111/203@QFN33 [CX4016]  
LPC1111@LQFP48 [CX3007]  
LPC1111@QFP44 [CX3005]  
LPC1111FDH20 [CX1033]  
LPC1112/101@QFN33 [CX4016]  
LPC1112/102@LQFP48 [CX3007]  
LPC1112/102@QFP44 [CX3005]  
LPC1112/103@QFN33 [CX4016]  
LPC1112/201@LQFP48 [CX3007]  
LPC1112/201@QFP44 [CX3005]  
LPC1112/202@QFN33 [CX4016]  
LPC1112/203@LQFP48 [CX3007]  
LPC1112/203@QFP44 [CX3005]  
LPC1112@QFN33 [CX4016]  
LPC1112FD20 [CX1033]  
LPC1113/101@LQFP48 [CX3007]  
LPC1113/101@QFP44 [CX3005]  
LPC1113/102@QFN33 [CX4016]  
LPC1113/103@LQFP48 [CX3007]  
LPC1113/103@QFP44 [CX3005]  
LPC1113/201@QFN33 [CX4016]  
LPC1113/202@LQFP48 [CX3007]  
LPC1113/202@QFP44 [CX3005]  
LPC1113/203@QFN33 [CX4016]  
LPC1113/301@QFN33 [CX4016]  
LPC1113/301@QFP48 [CX3007]  
LPC1113/302@QFP44 [CX3005]  
LPC1113/303@QFN33 [CX4016]  
LPC1113/303@QFP48 [CX3007]  
LPC1113@QFN33 [CX4016]  
LPC1113FD20 [CX1033]  
LPC1114/101@LQFP48 [CX3007]  
LPC1114/101@QFP44 [CX3005]  
LPC1114/102@QFN33 [CX4016]  
LPC1114/103@LQFP48 [CX3007]  
LPC1114/103@QFP44 [CX3005]  
LPC1114/201@QFN33 [CX4016]  
LPC1114/202@LQFP48 [CX3007]  
LPC1114/202@QFP44 [CX3005]  
LPC1114/203@QFN33 [CX4016]  
LPC1114/301@QFN33 [CX4016]  
LPC1114/301@QFP48 [CX3007]  
LPC1114/302@QFP44 [CX3005]  
LPC1114/303@QFN33 [CX4016]  
LPC1114/303@QFP48 [CX3007]  
LPC1114/323@QFP44 [CX3005]  
LPC1114/333@QFN33 [CX4016]  
LPC1114/333@QFP48 [CX3007]  
LPC1114@QFN33 [CX4016]



LPC1114@QFP44 [CX3005]  
LPC1114FDH20 [CX1033]  
LPC11A11/001@QFN33 [CX4016]  
LPC11A12/101@QFN33 [CX4016]  
LPC11A13/201@QFN33 [CX4016]  
LPC11A14/301@QFN33 [CX4016]  
LPC11C12/101@LQFP48 [CX3007]  
LPC11C12/103@LQFP48 [CX3007]  
LPC11C12/202@LQFP48 [CX3007]  
LPC11C12/301@LQFP48 [CX3007]  
LPC11C14/101@LQFP48 [CX3007]  
LPC11C14/103@LQFP48 [CX3007]  
LPC11C14/202@LQFP48 [CX3007]  
LPC11C14/301@LQFP48 [CX3007]  
LPC11C22/101@LQFP48 [CX3007]  
LPC11C22/103@LQFP48 [CX3007]  
LPC11C22/202@LQFP48 [CX3007]  
LPC11C22/301@LQFP48 [CX3007]  
LPC11C24/101@LQFP48 [CX3007]  
LPC11C24/103@LQFP48 [CX3007]  
LPC11C24/202@LQFP48 [CX3007]  
LPC11C24/301@LQFP48 [CX3007]  
LPC11D14FBD100 [CX3043]  
LPC11U34/311@QFN33 [CX4016]  
LPC11U35/301@BGA48 [BBBB]  
LPC11U35/301@QFP64 [CX3011]  
LPC11U35/401@QFP48 [CX3007]  
LPC11U35/501@BGA48 [BBBB]  
LPC11U35/501@QFP64 [CX3011]  
LPC11U36/301@QFP48 [CX3007]  
LPC11U36/401@BGA48 [BBBB]  
LPC11U36/401@QFP64 [CX3011]  
LPC11U36/501@QFP48 [CX3007]  
LPC11U37/301@BGA48 [BBBB]  
LPC11U37/301@QFP64 [CX3011]  
LPC11U37/401@QFP48 [CX3007]  
LPC11U37/501@BGA48 [BBBB]  
LPC11U37/501@QFP64 [CX3011]  
LPC1224/101@LQFP64 [CX3011]  
LPC1224/121@LQFP64 [CX3011]  
LPC1224/201@LQFP64 [CX3011]  
LPC1224/221@LQFP64 [CX3011]  
LPC1225/201@LQFP64 [CX3011]  
LPC1225/221@LQFP64 [CX3011]  
LPC1225/301@LQFP64 [CX3011]  
LPC1225/321@LQFP64 [CX3011]  
LPC1226/201@LQFP64 [CX3011]  
LPC1226/301@LQFP64 [CX3011]  
LPC1227/201@LQFP64 [CX3011]  
LPC1227/301@LQFP64 [CX3011]  
LPC12D27/201@LQFP48 [CX3007]  
LPC12D27/301@LQFP100 [CX3043]  
LPC12D27/301@LQFP64 [CX3011]  
LPC1311@QFN33 [CX4016]  
LPC1312@QFN33 [CX4016]  
LPC1313@QFN33 [CX4016]  
LPC1314@QFN33 [CX4016]  
LPC1341@QFN33 [CX4016]  
LPC1342@QFN33 [CX4016]

LPC1114FD20 [CX1033]  
LPC1115/303@QFP48 [CX3007]  
LPC11A11/001@QFP48 [CX3007]  
LPC11A12/101@QFP48 [CX3007]  
LPC11A13/201@QFP48 [CX3007]  
LPC11A14/301@QFP48 [CX3007]  
LPC11C12/102@LQFP48 [CX3007]  
LPC11C12/201@LQFP48 [CX3007]  
LPC11C12/203@LQFP48 [CX3007]  
LPC11C12@LQFP48 [CX3007]  
LPC11C14/102@LQFP48 [CX3007]  
LPC11C14/201@LQFP48 [CX3007]  
LPC11C14/203@LQFP48 [CX3007]  
LPC11C14@LQFP48 [CX3007]  
LPC11C22/102@LQFP48 [CX3007]  
LPC11C22/201@LQFP48 [CX3007]  
LPC11C22/203@LQFP48 [CX3007]  
LPC11C22@LQFP48 [CX3007]  
LPC11C24/102@LQFP48 [CX3007]  
LPC11C24/201@LQFP48 [CX3007]  
LPC11C24/203@LQFP48 [CX3007]  
LPC11C24@LQFP48 [CX3007]  
LPC11U33@QFN33 [CX4016]  
LPC11U34/421@QFN33 [CX4016]  
LPC11U35/301@QFP48 [CX3007]  
LPC11U35/401@BGA48 [BBBB]  
LPC11U35/401@QFP64 [CX3011]  
LPC11U35/501@QFP48 [CX3007]  
LPC11U36/301@BGA48 [BBBB]  
LPC11U36/301@QFP64 [CX3011]  
LPC11U36/401@QFP48 [CX3007]  
LPC11U36/501@BGA48 [BBBB]  
LPC11U36/501@QFP64 [CX3011]  
LPC11U37/301@QFP48 [CX3007]  
LPC11U37/401@BGA48 [BBBB]  
LPC11U37/401@QFP64 [CX3011]  
LPC11U37/501@QFP48 [CX3007]  
LPC1224/101@LQFP48 [CX3007]  
LPC1224/121@LQFP48 [CX3007]  
LPC1224/201@LQFP48 [CX3007]  
LPC1224/221@LQFP48 [CX3007]  
LPC1225/201@LQFP48 [CX3007]  
LPC1225/221@LQFP48 [CX3007]  
LPC1225/301@LQFP48 [CX3007]  
LPC1225/321@LQFP48 [CX3007]  
LPC1226/201@LQFP48 [CX3007]  
LPC1226/301@LQFP48 [CX3007]  
LPC1227/201@LQFP48 [CX3007]  
LPC1227/301@LQFP48 [CX3007]  
LPC12D27/201@LQFP100 [CX3043]  
LPC12D27/201@LQFP64 [CX3011]  
LPC12D27/301@LQFP48 [CX3007]  
LPC1311@LQFP48 [CX3007]  
LPC1312@LQFP48 [CX3007]  
LPC1313@LQFP48 [CX3007]  
LPC1314@LQFP48 [CX3007]  
LPC1341@LQFP48 [CX3007]  
LPC1342@LQFP48 [CX3007]  
LPC1343@LQFP48 [CX3007]

LPC1343@QFN33 [CX4016]                   LPC1344@LQFP48 [CX3007]  
LPC1344@QFN33 [CX4016]                   LPC1751@LQFP80 [CX3016]  
LPC1752@LQFP80 [CX3016]                  LPC1754@LQFP80 [CX3016]  
LPC1756@LQFP80 [CX3016]                  LPC1758@LQFP80 [CX3016]  
LPC1759@LQFP80 [CX3016]                  LPC1763@LQFP100 [CX3043]  
LPC1763FET100 [CX5055]                  LPC1764@LQFP100 [CX3043]  
LPC1764FET100 [CX5055]                  LPC1765@LQFP100 [CX3043]  
LPC1765FET100 [CX5055]                  LPC1766@LQFP100 [CX3043]  
LPC1766FET100 [CX5055]                  LPC1767@LQFP100 [CX3043]  
LPC1767FET100 [CX5055]                  LPC1768@LQFP100 [CX3043]  
LPC1768FET100 [CX5055]                  LPC1769@LQFP100 [CX3043]  
LPC1769FET100 [CX5055]                  LPC2101FBD48/00@LQFP48 [CX3007]  
LPC2101FBD48/01@LQFP48 [CX3007]        LPC2101FBD48@LQFP48 [CX3007]  
LPC2101FHN48/00@HVQFN48 [CX4021]       LPC2101FHN48/01@HVQFN48 [CX4021]  
LPC2101FHN48@HVQFN48 [CX4021]        LPC2102FBD48/00@LQFP48 [CX3007]  
LPC2102FBD48/01@LQFP48 [CX3007]        LPC2102FBD48@LQFP48 [CX3007]  
LPC2102FHN48/00@HVQFN48 [CX4021]       LPC2102FHN48/01@HVQFN48 [CX4021]  
LPC2102FHN48@HVQFN48 [CX4021]        LPC2103FA44@PLCC44 [CX2144]  
LPC2103FBD48/00@LQFP48 [CX3007]        LPC2103FBD48/01@LQFP48 [CX3007]  
LPC2103FBD48@LQFP48 [CX3007]        LPC2103FHN48/00@HVQFN48 [CX4021]  
LPC2103FHN48/01@HVQFN48 [CX4021]       LPC2103FHN48@HVQFN48 [CX4021]  
LPC2104BBD48@LQFP48 [CX3007]           LPC2104FBD48/00@LQFP48 [CX3007]  
LPC2104FBD48/01@LQFP48 [CX3007]        LPC2104FBD48@LQFP48 [CX3007]  
LPC2104FHN48/00@HVQFN48 [CX4021]       LPC2104FHN48/01@HVQFN48 [CX4021]  
LPC2104FHN48@HVQFN48 [CX4021]        LPC2105BBD48@LQFP48 [CX3007]  
LPC2105FBD48/00@LQFP48 [CX3007]        LPC2105FBD48/01@LQFP48 [CX3007]  
LPC2105FBD48@LQFP48 [CX3007]        LPC2105FHN48/00@HVQFN48 [CX4021]  
LPC2105FHN48/01@HVQFN48 [CX4021]       LPC2105FHN48@HVQFN48 [CX4021]  
LPC2106BBD48@LQFP48 [CX3007]           LPC2106FBD48/00@LQFP48 [CX3007]  
LPC2106FBD48/01@LQFP48 [CX3007]        LPC2106FBD48@LQFP48 [CX3007]  
LPC2106FHN48/00@HVQFN48 [CX4021]       LPC2106FHN48/01@HVQFN48 [CX4021]  
LPC2106FHN48@HVQFN48 [CX4021]        LPC2131FBD64@LQFP64 [CX3011]  
LPC2131FBD64@LQFP64(new) [CX3057-8]     LPC2131FHN64@QFN64(new) [CX4023]  
LPC2131FHN64@QFN64 [CX4023]           LPC2132FBD64@LQFP64 [CX3011]  
LPC2132FBD64@LQFP64 [CX3011]           LPC2132FBD64@LQFP64(new) [CX3057-8]  
LPC2132FBD64@LQFP64(new) [CX3057-8]    LPC2132FHN64@QFN64 [CX4023]           LPC2132FHN64@QFN64(new) [CX4023]  
LPC2132FHN64@QFN64 [CX4023]           LPC2134FBD64@LQFP64 [CX3011]  
LPC2134FBD64@LQFP64 [CX3011]           LPC2134FBD64@LQFP64(new) [CX3057-8]  
LPC2134FBD64@LQFP64(new) [CX3057-8]    LPC2134FHN64@QFN64 [CX4023]           LPC2134FHN64@QFN64(new) [CX4023]  
LPC2134FHN64@QFN64 [CX4023]           LPC2136FBD64@LQFP64 [CX3011]  
LPC2136FBD64@LQFP64 [CX3011]           LPC2136FBD64@LQFP64(new) [CX3057-8]  
LPC2136FBD64@LQFP64(new) [CX3057-8]    LPC2136FHN64@QFN64 [CX4023]           LPC2136FHN64@QFN64(new) [CX4023]  
LPC2136FHN64@QFN64 [CX4023]           LPC2138FBD64@LQFP64 [CX3011]  
LPC2138FBD64@LQFP64 [CX3011]           LPC2138FBD64@LQFP64(new) [CX3057-8]  
LPC2138FBD64@LQFP64(new) [CX3057-8]    LPC2138FHN64@QFN64 [CX4023]           LPC2138FHN64@QFN64(new) [CX4023]  
LPC2138FHN64@QFN64 [CX4023]           LPC2214FBD144@LQFP144 [CX3035]  
LPC2214FBD144@LQFP144 [CX3035]        P83C660X2@TQFP44 [CX3005]  
P83C660X2@TQFP44 [CX3005]           P83C661X2@PLCC44 [CX2044]  
P83C661X2@TQFP44 [CX3005]           P87C054@SDIP42 [CX0042]  
P87C054@SDIP42 [CX0042]           P87C51 [CX0001]  
P87C51@PLCC44 [CX2044]           P87C51@TQFP44 [CX3002]  
P87C51FA [CX0001]           P87C51FA@PLCC44 [CX2044]  
P87C51FA@TQFP44 [CX3002]           P87C51FB [CX0001]  
P87C51FB@PLCC44 [CX2044]           P87C51FB@TQFP44 [CX3002]  
P87C51FC [CX0001]           P87C51FC@PLCC44 [CX2044]  
P87C51FC@TQFP44 [CX3003]           P87C51MA2@PLCC44 [CX2044]  
P87C51MB2@PLCC44 [CX2044]           P87C51MC2@PLCC44 [CX2044]  
P87C51RA+ [CX0001]           P87C51RA+@PLCC44 [CX2044]  
P87C51RA+@TQFP44 [CX3003]           P87C51RA2 [CX0001]

P87C51RA2@PLCC44 [CX2044]  
P87C51RB+ [CX0001]  
P87C51RB+@TQFP44 [CX3003]  
P87C51RB2@PLCC44 [CX2044]  
P87C51RC+ [CX0001]  
P87C51RC+@TQFP44 [CX3003]  
P87C51RC2@PLCC44 [CX2044]  
P87C51RD+ [CX0001]  
P87C51RD+@TQFP44 [CX3003]  
P87C51RD2@PLCC44 [CX2044]  
P87C51SB [CX0001]  
P87C51SB@TQFP44 [CX3002]  
P87C51SF@PLCC44 [CX2044]  
P87C51UB [CX0001]  
P87C51UB@TQFP44 [CX3002]  
P87C51UF@PLCC44 [CX2044]  
P87C51X2 [CX0001]  
P87C51X2@TQFP44 [CX3005]  
P87C52 [CX0001]  
P87C52@TQFP44 [CX3002]  
P87C524@PLCC44 [CX2044]  
P87C528 [CX0001]  
P87C528@TQFP44 [CX3003]  
P87C52SB@PLCC44 [CX2044]  
P87C52SF [CX0001]  
P87C52SF@TQFP44 [CX3002]  
P87C52UB@PLCC44 [CX2044]  
P87C52UF [CX0001]  
P87C52UF@TQFP44 [CX3002]  
P87C52X2@PLCC44 [CX2044]  
P87C52X2@TTSOP38 [CX1049]  
P87C54@PLCC44 [CX2044]  
P87C54SB [CX0001]  
P87C54SB@TQFP44 [CX3002]  
P87C54SF@PLCC44 [CX2044]  
P87C54UB [CX0001]  
P87C54UB@TQFP44 [CX3002]  
P87C54UF@PLCC44 [CX2044]  
P87C54X2 [CX0001]  
P87C54X2@TQFP44 [CX3005]  
P87C550 [CX0001]  
P87C575 [CX0001]  
P87C575@TQFP44 [CX3002]  
P87C576@PLCC44 [CX2044]  
P87C58 [CX0001]  
P87C58@TQFP44 [CX3002]  
P87C58SB@PLCC44 [CX2044]  
P87C58UB [CX0001]  
P87C58UB@TQFP44 [CX3002]  
P87C58X2@PLCC44 [CX2044]  
P87C58X2@TTSOP38 [CX1049]  
P87C591@TQFP44 [CX3002]  
P87C652@PLCC44 [CX2044]  
P87C654 [CX0001]  
P87C654@TQFP44 [CX3002]  
P87C660X2@TQFP44 [CX3005]  
P87C661X2@TQFP44 [CX3005]  
P87C748@PLCC28 [CX2028]  
P87C749@PLCC28 [CX2028]

P87C51RA2@TQFP44 [CX3002]  
P87C51RB+@PLCC44 [CX2044]  
P87C51RB2 [CX0001]  
P87C51RB2@TQFP44 [CX3002]  
P87C51RC+@PLCC44 [CX2044]  
P87C51RC2 [CX0001]  
P87C51RC2@TQFP44 [CX3002]  
P87C51RD+@PLCC44 [CX2044]  
P87C51RD2 [CX0001]  
P87C51RD2@TQFP44 [CX3003]  
P87C51SB@PLCC44 [CX2044]  
P87C51SF [CX0001]  
P87C51SF@TQFP44 [CX3002]  
P87C51UB@PLCC44 [CX2044]  
P87C51UF [CX0001]  
P87C51UF@TQFP44 [CX3002]  
P87C51X2@PLCC44 [CX2044]  
P87C51X2@TTSOP38 [CX1049]  
P87C52@PLCC44 [CX2044]  
P87C524 [CX0001]  
P87C524@TQFP44 [CX3003]  
P87C528@PLCC44 [CX2044]  
P87C52SB [CX0001]  
P87C52SB@TQFP44 [CX3002]  
P87C52SF@PLCC44 [CX2044]  
P87C52UB [CX0001]  
P87C52UB@TQFP44 [CX3002]  
P87C52UF@PLCC44 [CX2044]  
P87C52X2 [CX0001]  
P87C52X2@TQFP44 [CX3005]  
P87C54 [CX0001]  
P87C54@TQFP44 [CX3002]  
P87C54SB@PLCC44 [CX2044]  
P87C54SF [CX0001]  
P87C54SF@TQFP44 [CX3002]  
P87C54UB@PLCC44 [CX2044]  
P87C54UF [CX0001]  
P87C54UF@TQFP44 [CX3002]  
P87C54X2@PLCC44 [CX2044]  
P87C54X2@TTSOP38 [CX1049]  
P87C550@PLCC44 [CX2044]  
P87C575@PLCC44 [CX2044]  
P87C576 [CX0001]  
P87C576@TQFP44 [CX3002]  
P87C58@PLCC44 [CX2044]  
P87C58SB [CX0001]  
P87C58SB@TQFP44 [CX3002]  
P87C58UB@PLCC44 [CX2044]  
P87C58X2 [CX0001]  
P87C58X2@TQFP44 [CX3005]  
P87C591@PLCC44 [CX2044]  
P87C652 [CX0001]  
P87C652@TQFP44 [CX3002]  
P87C654@PLCC44 [CX2044]  
P87C660X2@PLCC44 [CX2044]  
P87C661X2@PLCC44 [CX2044]  
P87C748 [CX0001]  
P87C749 [CX0001]  
P87C750 [CX0001]

P87C750@PLCC28 [CX2028]  
P87C751 [CX0001]  
P87C751@SSOP24 [CX1026]  
P87C752@PLCC28 [CX2028]  
P87C754 [CX0001]  
P87C754@SSOP28 [CX1026]  
P87CL52X2@PLCC44 [CX2044]  
P87CL52X2@TTSOP38 [CX1049]  
P87CL54X2@PLCC44 [CX2044]  
P87CL54X2@TTSOP38 [CX1049]  
P87L51FA@PLCC44 [CX2044]  
P87L51FB [CX0001]  
P87L51FB@TQFP44 [CX3002]  
P87LPC759(ISP) [CX0001]  
P87LPC760(ISP) [CX0001]  
P87LPC760@TSSOP14(ISP) [CX0001]  
P87LPC761(ISP) [CX0001]  
P87LPC762(ISP) [CX0001]  
P87LPC762@PLCC44(ISP) [CX0001]  
P87LPC762@SOIC20(ISP) [CX0001]  
P87LPC764(ISP) [CX0001]  
P87LPC764@PLCC44(ISP) [CX0001]  
P87LPC764@SOIC20(ISP) [CX0001]  
P87LPC764@TSSOP20(ISP) [CX0001]  
P87LPC767(ISP) [CX0001]  
P87LPC767@PLCC44(ISP) [CX0001]  
P87LPC767@SOIC20(ISP) [CX0001]  
P87LPC768(ISP) [CX0001]  
P87LPC768@SOIC20(ISP) [CX0001]  
P87LPC769(ISP) [CX0001]  
P87LPC769@PLCC44(ISP) [CX0001]  
P87LPC769@SOIC20(ISP) [CX0001]  
P87LPC778(ISP) [CX0001]  
P87LPC778@TSSOP20(ISP) [CX0001]  
P87LPC779(ISP) [CX0001]  
P87LPC779@TSSOP20(ISP) [CX0001]  
P89C138@PLCC44 [CX2044]  
P89C238 [CX0001]  
P89C238@TQFP44 [CX3005]  
P89C51B@PLCC44 [CX2044]  
P89C51RA+ [CX0001]  
P89C51RA+@TQFP44 [CX3005]  
P89C51RA2B@PLCC44 [CX2044]  
P89C51RB+ [CX0001]  
P89C51RB+@TQFP44 [CX3005]  
P89C51RB2B@PLCC44 [CX2044]  
P89C51RB2H [CX0001]  
P89C51RB2H@TQFP44 [CX3002]  
P89C51RC+@PLCC44 [CX2044]  
P89C51RC2B [CX0001]  
P89C51RC2B@TQFP44 [CX3005]  
P89C51RC2H@PLCC44 [CX2044]  
P89C51RD+ [CX0001]  
P89C51RD+@TQFP44 [CX3005]  
P89C51RD2B@PLCC44 [CX2044]  
P89C51RD2H [CX0001]  
P89C51RD2H@TQFP44 [CX3002]  
P89C51UB@PLCC44 [CX2044]  
P89C51UF [CX0001]

P87C750@SSOP24 [CX1026]  
P87C751@PLCC28 [CX2028]  
P87C752 [CX0001]  
P87C752@SSOP28 [CX1026]  
P87C754@PLCC28 [CX2028]  
P87CL52X2 [CX0001]  
P87CL52X2@TQFP44 [CX3005]  
P87CL54X2 [CX0001]  
P87CL54X2@TQFP44 [CX3005]  
P87L51FA [CX0001]  
P87L51FA@TQFP44 [CX3002]  
P87L51FB@PLCC44 [CX2044]  
P87LPC759 [CX0001]  
P87LPC760 [CX0001]  
P87LPC760@TSSOP14 [CX1000]  
P87LPC761 [CX0001]  
P87LPC762 [CX0001]  
P87LPC762@PLCC44 [CX1044]  
P87LPC762@SOIC20 [CX1033]  
P87LPC764 [CX0001]  
P87LPC764@PLCC44 [CX1044]  
P87LPC764@SOIC20 [CX1033]  
P87LPC764@TSSOP20 [CX1001]  
P87LPC767 [CX0001]  
P87LPC767@PLCC44 [CX1044]  
P87LPC767@SOIC20 [CX1033]  
P87LPC768 [CX0001]  
P87LPC768@SOIC20 [CX1033]  
P87LPC769 [CX0001]  
P87LPC769@PLCC44 [CX1044]  
P87LPC769@SOIC20 [CX1033]  
P87LPC778 [CX0001]  
P87LPC778@TSSOP20 [CX1000]  
P87LPC779 [CX0001]  
P87LPC779@TSSOP20 [CX1000]  
P89C138 [CX0001]  
P89C138@TQFP44 [CX3005]  
P89C238@PLCC44 [CX2044]  
P89C51B [CX0001]  
P89C51B@TQFP44 [CX3005]  
P89C51RA+@PLCC44 [CX2044]  
P89C51RA2B [CX0001]  
P89C51RA2B@TQFP44 [CX3005]  
P89C51RB+@PLCC44 [CX2044]  
P89C51RB2B [CX0001]  
P89C51RB2B@TQFP44 [CX3005]  
P89C51RB2H@PLCC44 [CX2044]  
P89C51RC+ [CX0001]  
P89C51RC+@TQFP44 [CX3005]  
P89C51RC2B@PLCC44 [CX2044]  
P89C51RC2H [CX0001]  
P89C51RC2H@TQFP44 [CX3002]  
P89C51RD+@PLCC44 [CX2044]  
P89C51RD2B [CX0001]  
P89C51RD2B@TQFP44 [CX3005]  
P89C51RD2H@PLCC44 [CX2044]  
P89C51UB [CX0001]  
P89C51UB@TQFP44 [CX3005]  
P89C51UF@PLCC44 [CX2044]

P89C51UF@TQFP44 [CX3005]  
P89C51X2@PLCC44 [CX2044]  
P89C51X2B [CX0001]  
P89C51X2B@TQFP44 [CX3005]  
P89C51X2F@PLCC44 [CX2044]  
P89C52 [CX0001]  
P89C52@TQFP44 [CX3005]  
P89C52B@PLCC44 [CX2044]  
P89C52UB [CX0001]  
P89C52UB@TQFP44 [CX3005]  
P89C52UF@PLCC44 [CX2044]  
P89C52X2 [CX0001]  
P89C52X2@TQFP44 [CX3005]  
P89C52X2B@PLCC44 [CX2044]  
P89C52X2F [CX0001]  
P89C52X2F@TQFP44 [CX3005]  
P89C538@PLCC44 [CX2044]  
P89C54@PLCC44 [CX2044]  
P89C54B [CX0001]  
P89C54B@TQFP44 [CX3005]  
P89C54UB@PLCC44 [CX2044]  
P89C54UF [CX0001]  
P89C54UF@TQFP44 [CX3005]  
P89C54X2@PLCC44 [CX2044]  
P89C54X2B [CX0001]  
P89C54X2B@TQFP44 [CX3005]  
P89C54X2F@PLCC44 [CX2044]  
P89C58 [CX0001]  
P89C58@TQFP44 [CX3005]  
P89C58B@PLCC44 [CX2044]  
P89C58UB [CX0001]  
P89C58UB@TQFP44 [CX3005]  
P89C58UF@PLCC44 [CX2044]  
P89C58X2 [CX0001]  
P89C58X2@TQFP44 [CX3005]  
P89C58X2B@PLCC44 [CX2044]  
P89C58X2F [CX0001]  
P89C58X2F@TQFP44 [CX3005]  
P89C60X2@PLCC44 [CX2044]  
P89C61X2 [CX0001]  
P89C61X2@TQFP44 [CX3005]  
P89C660@PLCC44 [CX2044]  
P89C662 [CX0001]  
P89C662@TQFP44 [CX3002]  
P89C664@PLCC44 [CX2044]  
P89C668 [CX0001]  
P89C668@TQFP44 [CX3002]  
P89C669@LQFP44 [CX3005]  
P89C669X2 [CX0001]  
P89C669X2@PLCC44 [CX2044]  
P89C738@PLCC44 [CX2044]  
P89C838 [CX0001]  
P89C838@TQFP44 [CX3005]  
P89CV51RB2@TQFP44 [CX3005]  
P89CV51RC2@TQFP44 [CX3005]  
P89CV51RD2@TQFP44 [CX3005]  
P89LPC901(FD)(ISP) [CX0001]  
P89LPC901(FN)(ISP) [CX0001]  
P89LPC902(FD)(ISP) [CX0001]

P89C51X2 [CX0001]  
P89C51X2@TQFP44 [CX3005]  
P89C51X2B@PLCC44 [CX2044]  
P89C51X2F [CX0001]  
P89C51X2F@TQFP44 [CX3005]  
P89C52@PLCC44 [CX2044]  
P89C52B [CX0001]  
P89C52B@TQFP44 [CX3005]  
P89C52UB@PLCC44 [CX2044]  
P89C52UF [CX0001]  
P89C52UF@TQFP44 [CX3005]  
P89C52X2@PLCC44 [CX2044]  
P89C52X2B [CX0001]  
P89C52X2B@TQFP44 [CX3005]  
P89C52X2F@PLCC44 [CX2044]  
P89C536@PLCC44 [CX2044]  
P89C54 [CX0001]  
P89C54@TQFP44 [CX3005]  
P89C54B@PLCC44 [CX2044]  
P89C54UB [CX0001]  
P89C54UB@TQFP44 [CX3005]  
P89C54UF@PLCC44 [CX2044]  
P89C54X2 [CX0001]  
P89C54X2@TQFP44 [CX3005]  
P89C54X2B@PLCC44 [CX2044]  
P89C54X2F [CX0001]  
P89C54X2F@TQFP44 [CX3005]  
P89C58@PLCC44 [CX2044]  
P89C58B [CX0001]  
P89C58B@TQFP44 [CX3005]  
P89C58UB@PLCC44 [CX2044]  
P89C58UF [CX0001]  
P89C58UF@TQFP44 [CX3005]  
P89C58X2@PLCC44 [CX2044]  
P89C58X2B [CX0001]  
P89C58X2B@TQFP44 [CX3005]  
P89C58X2F@PLCC44 [CX2044]  
P89C60X2 [CX0001]  
P89C60X2@TQFP44 [CX3005]  
P89C61X2@PLCC44 [CX2044]  
P89C660 [CX0001]  
P89C660@TQFP44 [CX3002]  
P89C662@PLCC44 [CX2044]  
P89C664 [CX0001]  
P89C664@TQFP44 [CX3002]  
P89C668@PLCC44 [CX2044]  
P89C669 [CX0001]  
P89C669@PLCC44 [CX2044]  
P89C669X2@LQFP44 [CX3005]  
P89C738 [CX0001]  
P89C738@TQFP44 [CX3005]  
P89C838@PLCC44 [CX2044]  
P89CV51RB2@PLCC44 [CX2044]  
P89CV51RC2@PLCC44 [CX2044]  
P89CV51RD2@PLCC44 [CX2044]  
P89LPC901(FD) [CX1045]  
P89LPC901(FN) [CX0001]  
P89LPC902(FD) [CX1045]  
P89LPC902(FN) [CX0001]

P89LPC902(FN)(ISP) [CX0001] P89LPC903(FD) [CX1045]  
P89LPC903(FD)(ISP) [CX0001] P89LPC904(FD) [CX1045]  
P89LPC904(FD)(ISP) [CX0001] P89LPC904(FN) [CX0001]  
P89LPC904(FN)(ISP) [CX0001] P89LPC906(FD) [CX1045]  
P89LPC906(FD)(ISP) [CX0001] P89LPC907(FD) [CX1045]  
P89LPC907(FD)(ISP) [CX0001] P89LPC908(FD) [CX1045]  
P89LPC908(FD)(ISP) [CX0001] P89LPC9102(FTK)@HVSON10 [CX4007]  
P89LPC9103(FTK)@HVSON10 [CX4007] P89LPC9107(FDH)@TSSOP14 [CX1001]  
P89LPC9107(FN) [CX3001] P89LPC912(FDH)@TSSOP14 [CX1000]  
P89LPC912(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC913(FDH)@TSSOP14 [CX1000]  
P89LPC913(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC914(FDH)@TSSOP14 [CX1000]  
P89LPC914(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC915(FDH)@TSSOP14 [CX1000]  
P89LPC915(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC916(FDH)@TSSOP16 [CX1000]  
P89LPC916(FDH)@TSSOP16(ISP) [CX0001]  
P89LPC917(FDH)@TSSOP16 [CX1000]  
P89LPC917(FDH)@TSSOP16(ISP) [CX0001]  
P89LPC920(FDH)@TSSOP20 [CX1000]  
P89LPC920(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC920(FN) [CX0001] P89LPC920(FN)(ISP) [CX0001]  
P89LPC9201(FDH)@TSSOP20 [CX1000]  
P89LPC9201(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9201(FN) [CX0001] P89LPC9201(FN)(ISP) [CX0001]  
P89LPC920A1(FDH)@TSSOP20 [CX1000]  
P89LPC920A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC920A1(FN) [CX0001] P89LPC920A1(FN)(ISP) [CX0001]  
P89LPC921(FDH)@TSSOP20 [CX1000]  
P89LPC921(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC921(FN) [CX0001] P89LPC921(FN)(ISP) [CX0001]  
P89LPC9211(FDH)@TSSOP20 [CX1000]  
P89LPC9211(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9211(FN) [CX0001] P89LPC9211(FN)(ISP) [CX0001]  
P89LPC921A1(FDH)@TSSOP20 [CX1000]  
P89LPC921A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC921A1(FN) [CX0001] P89LPC921A1(FN)(ISP) [CX0001]  
P89LPC922(FDH)@TSSOP20 [CX1000]  
P89LPC922(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC922(FN) [CX0001] P89LPC922(FN)(ISP) [CX0001]  
P89LPC9221(FDH)@TSSOP20 [CX1000]  
P89LPC9221(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9221(FN) [CX0001] P89LPC9221(FN)(ISP) [CX0001]  
P89LPC9221A1(FDH)@TSSOP20 [CX1000]  
P89LPC9221A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9221A1(FN) [CX0001] P89LPC9221A1(FN)(ISP) [CX0001]  
P89LPC922A1(FDH)@TSSOP20 [CX1000]  
P89LPC922A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC922A1(FN) [CX0001] P89LPC922A1(FN)(ISP) [CX0001]  
P89LPC924(FDH)@TSSOP20 [CX1000]  
P89LPC924(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC924(FN) [CX0001] P89LPC924(FN)(ISP) [CX0001]  
P89LPC9241(FDH)@TSSOP20 [CX1000]  
P89LPC9241(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9241(FN) [CX0001] P89LPC9241(FN)(ISP) [CX0001]  
P89LPC924A1(FDH)@TSSOP20 [CX1000]  
P89LPC924A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC924A1(FN) [CX0001] P89LPC924A1(FN)(ISP) [CX0001]

P89LPC925(FDH)@TSSOP20 [CX1000]  
P89LPC925(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC925(FN) [CX0001] P89LPC925(FN)(ISP) [CX0001]  
P89LPC9251(FDH)@TSSOP20 [CX1000]  
P89LPC9251(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9251(FN) [CX0001] P89LPC9251(FN)(ISP) [CX0001]  
P89LPC925A1(FDH)@TSSOP20 [CX1000]  
P89LPC925A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC925A1(FN) [CX0001] P89LPC925A1(FN)(ISP) [CX0001]  
P89LPC930(BA)@PLCC28 [CX2028]  
P89LPC930(BA)@PLCC28(ISP) [CX0001]  
P89LPC930(BDH)@TSSOP28 [CX1001]  
P89LPC930(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC9301(BA)@PLCC28 [CX2028] P89LPC9301(BDH)@TSSOP28 [CX1001]  
P89LPC9301FA [CX2028] P89LPC9301FDH [CX1001]  
P89LPC930FA [CX2028] P89LPC930FDH [CX1001]  
P89LPC931(BA)@PLCC28 [CX2028]  
P89LPC931(BA)@PLCC28(ISP) [CX0001]  
P89LPC931(BDH)@TSSOP28 [CX1001]  
P89LPC931(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC9311(BA)@PLCC28 [CX2028] P89LPC9311(BDH)@TSSOP28 [CX1001]  
P89LPC9311FA [CX2028] P89LPC9311FDH [CX1001]  
P89LPC931FA [CX2028] P89LPC931FDH [CX1001]  
P89LPC932(BA)@PLCC28 [CX2028] P89LPC932(BDH)@TSSOP28 [CX1001]  
P89LPC932(FA)@PLCC28 [CX2028] P89LPC93201BA@PLCC28 [CX2028]  
P89LPC93201BDH@TSSOP28 [CX1001] P89LPC93201FA@PLCC28 [CX2028]  
P89LPC93201FDH@TSSOP28 [CX1001] P89LPC93201FHN@QFN28 [CX4014]  
P89LPC9321BA@PLCC28 [CX2028] P89LPC9321BDH@TSSOP28 [CX1001]  
P89LPC9321FA@PLCC28 [CX2028] P89LPC9321FDH@TSSOP28 [CX1001]  
P89LPC9321FHN@QFN28 [CX4014] P89LPC932A1(BA)@PLCC28 [CX2028]  
P89LPC932A1(BA)@PLCC28(ISP) [CX0001]  
P89LPC932A1(BDH)@TSSOP28 [CX1001]  
P89LPC932A1(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC932A1(FA)@PLCC28 [CX2028]  
P89LPC932A1(FDH)@TSSOP28 [CX1001]  
P89LPC932A1(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC932A1(FHN)@HVQFN28 [CX4014]  
P89LPC932A1(FHN)@HVQFN28(ISP) [CX0001]  
P89LPC933(BDH)@TSSOP28 [CX1001]  
P89LPC933(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC933(FDH)@TSSOP28 [CX1001]  
P89LPC933(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC933(HDH)@TSSOP28 [CX1001] P89LPC9331(BDH)@TSSOP28 [CX1001]  
P89LPC9331(FDH)@TSSOP28 [CX1001] P89LPC9331(HDH)@TSSOP28 [CX1001]  
P89LPC934(BDH)@TSSOP28 [CX1001]  
P89LPC934(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC934(FDH)@TSSOP28 [CX1001]  
P89LPC934(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC93401(FDH)@TSSOP28 [CX1001]  
P89LPC93401V [CX0001] P89LPC9341(BDH)@TSSOP28 [CX1001]  
P89LPC9341(FDH)@TSSOP28 [CX1001] P89LPC9341V [CX0001]  
P89LPC935(BA)@PLCC28 [CX2028]  
P89LPC935(BA)@PLCC28(ISP) [CX0001]  
P89LPC935(BDH)@TSSOP28 [CX1001]  
P89LPC935(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC935(FA)@PLCC28 [CX2028]  
P89LPC935(FA)@PLCC28(ISP) [CX0001]  
P89LPC935(FDH)@TSSOP28 [CX1001]  
P89LPC935(FDH)@TSSOP28(ISP) [CX0001]

P89LPC935(FHN)@HVQFN28 [CX4014]  
P89LPC935(FHN)@HVQFN28(ISP) [CX0001]  
P89LPC93501BA@PLCC28 [CX2028] P89LPC93501BDH@TSSOP28 [CX1001]  
P89LPC93501FA@PLCC28 [CX2028] P89LPC93501FDH@TSSOP28 [CX1001]  
P89LPC93501FHN@QFN28 [CX4014] P89LPC9351BA@PLCC28 [CX2028]  
P89LPC9351BDH@TSSOP28 [CX1001] P89LPC9351FA@PLCC28 [CX2028]  
P89LPC9351FDH@TSSOP28 [CX1001] P89LPC9351FHN@QFN28 [CX4014]  
P89LPC936(FA)@PLCC28 [CX2028] P89LPC936(FDH)@TSSOP28 [CX1001]  
P89LPC9361(FA)@PLCC28 [CX2028] P89LPC9361(FDH)@TSSOP28 [CX1001]  
P89LPC938(FA)@PLCC28 [CX2028]  
P89LPC938(FA)@PLCC28(ISP) [CX0001]  
P89LPC938(FDH)@TSSOP28 [CX1001]  
P89LPC938(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC938(FHN)@HVQFN28 [CX4014]  
P89LPC938(FHN)@HVQFN28(ISP) [CX0001]  
P89LPC93801BA@PLCC28 [CX2028] P89LPC93801BDH@TSSOP28 [CX1001]  
P89LPC93801FA@PLCC28 [CX2028] P89LPC93801FDH@TSSOP28 [CX1001]  
P89LPC93801FHN@QFN28 [CX4014] P89LPC9381BA@PLCC28 [CX2028]  
P89LPC9381BDH@TSSOP28 [CX1001] P89LPC9381FA@PLCC28 [CX2028]  
P89LPC9381FDH@TSSOP28 [CX1001] P89LPC9381FHN@QFN28 [CX4014]  
P89LPC9401(FBD)@LQFP64(ISP) [CX0001]  
P89LPC9408(FBD)@LQFP64(ISP) [CX0001]  
P89LPC952@LQFP44 [CX3005] P89LPC952@LQFP44(ISP) [CX0001]  
P89LPC952@LQFP48 [CX3007] P89LPC952@LQFP48(ISP) [CX0001]  
P89LPC952@PLCC44 [CX2044] P89LPC952@PLCC44(ISP) [CX0001]  
P89LPC954@LQFP44 [CX3005] P89LPC954@LQFP44(ISP) [CX0001]  
P89LPC954@LQFP48 [CX3007] P89LPC954@LQFP48(ISP) [CX0001]  
P89LPC954@PLCC44 [CX2044] P89LPC954@PLCC44(ISP) [CX0001]  
P89LPC970FDH@TSSOP20 [CX1000]  
P89LPC970FDH@TSSOP20(serial) [CX1000]  
P89LPC970FN [CX0001] P89LPC970FN(serial) [CX0001]  
P89LPC971FDH@TSSOP20 [CX1000]  
P89LPC971FDH@TSSOP20(serial) [CX1000]  
P89LPC971FN [CX0001] P89LPC971FN(serial) [CX0001]  
P89LPC972FDH@TSSOP20 [CX1000]  
P89LPC972FDH@TSSOP20(serial) [CX1000]  
P89LPC972FN [CX0001] P89LPC972FN(serial) [CX0001]  
P89LPC980FDH@TSSOP28 [CX1001]  
P89LPC980FDH@TSSOP28(serial) [CX1001]  
P89LPC982FDH@TSSOP28 [CX1001]  
P89LPC982FDH@TSSOP28(serial) [CX1001]  
P89LPC983FA@PLCC28 [CX2028]  
P89LPC983FA@PLCC28(serial) [CX2028]  
P89LPC983FDH@TSSOP28 [CX1001]  
P89LPC983FDH@TSSOP28(serial) [CX1001]  
P89LPC985FA@PLCC28 [CX2028]  
P89LPC985FA@PLCC28(serial) [CX2028]  
P89LPC985FDH@TSSOP28 [CX1001]  
P89LPC985FDH@TSSOP28(serial) [CX1001]  
P89LPC9902FTK [CX4047] P89LPC9903FTK [CX4047]  
P89LV51RB2 [CX0001] P89LV51RB2@PLCC44 [CX2044]  
P89LV51RB2@TQFP44 [CX3005] P89LV51RB2FA@PLCC44 [CX2044]  
P89LV51RB2FBC@TQFP44 [CX3005] P89LV51RB2FN [CX0001]  
P89LV51RC2 [CX0001] P89LV51RC2@PLCC44 [CX2044]  
P89LV51RC2@TQFP44 [CX3005] P89LV51RC2FA@PLCC44 [CX2044]  
P89LV51RC2FBC@TQFP44 [CX3005] P89LV51RC2FN [CX0001]  
P89LV51RD2 [CX0001] P89LV51RD2(new) [CX0001]  
P89LV51RD2(new)@PLCC44 [CX2044] P89LV51RD2(new)@TQFP44 [CX3005]  
P89LV51RD2@PLCC44 [CX2044] P89LV51RD2@TQFP44 [CX3005]



P89LV51RD2BA(new)@PLCC44 [CX2044]  
P89LV51RD2BA@PLCC44 [CX2044]  
P89LV51RD2BBC(new)@TQFP44 [CX3005]  
P89LV51RD2BBC@TQFP44 [CX3005] P89LV51RD2BN [CX0001]  
P89LV51RD2BN(new) [CX0001]  
P89LV51RD2FA(new)@PLCC44 [CX2044]  
P89LV51RD2FA@PLCC44 [CX2044]  
P89LV51RD2FBC(new)@TQFP44 [CX3005]  
P89LV51RD2FBC@TQFP44 [CX3005] P89LV51RD2FN [CX0001]  
P89LV51RD2FN(new) [CX0001] P89V51RB2 [CX0001]  
P89V51RB2@PLCC44 [CX2044] P89V51RB2@TQFP44 [CX3005]  
P89V51RB2FA@PLCC44 [CX2044] P89V51RB2FBC@TQFP44 [CX3005]  
P89V51RB2FN [CX0001] P89V51RC2 [CX0001]  
P89V51RC2@PLCC44 [CX2044] P89V51RC2@TQFP44 [CX3005]  
P89V51RC2FA@PLCC44 [CX2044] P89V51RC2FBC@TQFP44 [CX3005]  
P89V51RC2FN [CX0001] P89V51RD2 [CX0001]  
P89V51RD2(new) [CX0001] P89V51RD2(new)@PLCC44 [CX2044]  
P89V51RD2(new)@TQFP44 [CX3005] P89V51RD2@PLCC44 [CX2044]  
P89V51RD2@TQFP44 [CX3005] P89V51RD2BA(new)@PLCC44 [CX2044]  
P89V51RD2BA@PLCC44 [CX2044]  
P89V51RD2BBC(new)@TQFP44 [CX3005]  
P89V51RD2BBC@TQFP44 [CX3005] P89V51RD2BN [CX0001]  
P89V51RD2BN(new) [CX0001] P89V51RD2FA(new)@PLCC44 [CX2044]  
P89V51RD2FA@PLCC44 [CX2044]  
P89V51RD2FBC(new)@TQFP44 [CX3005]  
P89V51RD2FBC@TQFP44 [CX3005]  
P89V51RD2FN(new) [CX0001] P89V51RD2FN [CX0001]  
P89V52X2(ISP) [CX0001] P89V52X2 [CX0001]  
P89V52X2@PLCC44(ISP) [CX0001] P89V52X2@PLCC44 [CX2044]  
P89V52X2@TQFP44(ISP) [CX0001] P89V52X2@TQFP44 [CX3005]  
P89V54X2(ISP) [CX0001] P89V54X2 [CX0001]  
P89V54X2@PLCC44(ISP) [CX0001] P89V54X2@PLCC44 [CX2044]  
P89V54X2@TQFP44(ISP) [CX0001] P89V54X2@TQFP44 [CX3005]  
P89V660@TQFP44 [CX3005] P89V660@PLCC44 [CX2044]  
P89V662@TQFP44 [CX3005] P89V662@PLCC44 [CX2044]  
P89V664@TQFP44 [CX3005] P89V664@PLCC44 [CX2044]  
PCF7953AC1500@TSSOP28 [CX1001]  
PXAC37@PLCC44 [CX2044] PXAC37@TQFP44 [CX3003]  
PXAG17@PLCC44 [CX2044] PXAG17@TQFP44 [CX3003]  
PXAG27@PLCC44 [CX2044] PXAG27@TQFP44 [CX3003]  
PXAG37@PLCC44 [CX2044] PXAG37@TQFP44 [CX3003]  
PXAG39@PLCC44 [CX2044] PXAG39@TQFP44 [CX3003]  
PXAG39K@PLCC44 [CX2044] PXAG39K@TQFP44 [CX3003]  
PXAG49@PLCC44 [CX2044] PXAG49@TQFP44 [CX3003]  
PXAG49K@PLCC44 [CX2044] PXAG49K@TQFP44 [CX3003]  
TDA11105PS@SDIP64 [CX0064] TDA11106PS@SDIP64 [CX0064]  
TDA11112PS@SDIP64 [CX0064] TDA11115PS@SDIP64 [CX0064]  
TDA11116PS@SDIP64 [CX0064] TDA11125PS@SDIP64 [CX0064]  
TDA11126PS@SDIP64 [CX0064] TDA11135PS@SDIP64 [CX0064]  
TDA11136PS@SDIP64 [CX0064] TDA11142PS@SDIP64 [CX0064]  
TDA11145PS@SDIP64 [CX0064] TDA11146PS@SDIP64 [CX0064]  
TDA11155PS@SDIP64 [CX0064] TDA11156PS@SDIP64 [CX0064]  
TDA12135PS@SDIP64 [CX0064] TDA12136PS@SDIP64 [CX0064]  
TDA12155PS@SDIP64 [CX0064] TDA12156PS@SDIP64 [CX0064]  
TDA12165PS@SDIP64 [CX0064] TDA12166PS@SDIP64 [CX0064]  
TDA12175PS@SDIP64 [CX0064] TDA12176PS@SDIP64 [CX0064]  
TDA12185PS@SDIP64 [CX0064] TDA12186PS@SDIP64 [CX0064]  
TDA12195PS@SDIP64 [CX0064] TDA12196PS@SDIP64 [CX0064]

# OKI

## E (E) PROM/FRAM/NVRAM

MR27V1652E@PSOP44 [CX1014]	MR27V401D [CX0001]
MR27V401D@PSOP32 [CX1014]	MR27V401D@TSOP32 [CX1003]
MR27V401E [CX0001]	MR27V401E@PSOP32 [CX1014]
MR27V401E@TSOP32 [CX1003]	MR27V402D [CX0001]
MR27V402D@PSOP40 [CX1022]	MR27V402D@TSOP44 [CX1014]
MR27V402E [CX0001]	MR27V402E@PSOP40 [CX1022]
MR27V402E@TSOP44 [CX1014]	MR27V802F@PSOP44 [CX1014]
MR27V802F@TSOP44 [CX1010]	MR27V802F@TSOP48 [CX1004]
MSM16812(08bit) [CX0001]	MSM16812(08bit)@SOIC8 [CX1045]
MSM271000 [CX0001]	MSM271000@PLCC32 [CX2032]
MSM271000@TSOP32 [CX1002]	MSM271000AS [CX0001]
MSM271000AS@PLCC32 [CX2032]	MSM271000AS@TSOP32 [CX1002]
MSM27128 [CX0001]	MSM27128A [CX0001]
MSM27128AS [CX0001]	MSM27128AZB-RS [CX0001]
MSM2716 [CX0001]	MSM27256 [CX0001]
MSM27256AS [CX0001]	MSM27256ZB-RS [CX0001]
MSM2732 [CX0001]	MSM2732A [CX0001]
MSM27512 [CX0001]	MSM27512AS [CX0001]
MSM27512ZB-RS [CX0001]	MSM2764 [CX0001]
MSM2764A [CX0001]	MSM2764AS [CX0001]
MSM2764AZB-RS [CX0001]	MSM2764RS [CX0001]
MSM27C1024 [CX0001]	MSM27C1024AS [CX0001]
MSM27C128 [CX0001]	MSM27C128AZB-RS [CX0001]
MSM27C256 [CX0001]	MSM27C256A [CX0001]
MSM27C256H [CX0001]	MSM27C256HZB [CX0001]
MSM27C256ZB [CX0001]	MSM27C64AS [CX0001]
MSM27C802CZ [CX0001]	MSM27C802CZ@PSOP44 [CX1014]
MSM27C802CZ@TSOP44 [CX1011]	MSM2816A(RS) [CX0001]
MSM28C16A [CX0001]	

## DRAM & SRAM

MSM51256 [CX0001]	MSM51256@SOIC28 [CX1035]
MSM51257AL [CX0001]	MSM51257AL@SOIC28 [CX1035]
MSM51257ALL [CX0001]	MSM51257ALL@SOIC28 [CX1035]
MSM5165AL [CX0001]	MSM5165AL@SOIC28 [CX1035]

# ON Semiconductor

## E (E) PROM/FRAM/NVRAM

CAT13001(08bit)@SOIC8 [CX1045]	CAT13001(16bit)@SOIC8 [CX1045]
CAT13004(08bit)@SOIC8 [CX1045]	CAT13004(16bit)@SOIC8 [CX1045]
CAT13008(08bit)@SOIC8 [CX1045]	CAT13008(16bit)@SOIC8 [CX1045]
CAT13016(08bit)@SOIC8 [CX1045]	CAT13016(16bit)@SOIC8 [CX1045]
CAT1320 [CX0001]	CAT1320@SOIC8 [CX1045]
CAT1320@TDFN8 [CX0001]	CAT1320@TSSOP8 [CX1059]
CAT1321 [CX0001]	CAT1321@SOIC8 [CX1045]
CAT1321@TDFN8 [CX0001]	CAT1321@TSSOP8 [CX1059]
CAT14002@SOIC8 [CX1045]	CAT14004@SOIC8 [CX1045]
CAT14008@SOIC8 [CX1045]	CAT14016@SOIC8 [CX1045]
CAT15002@SOIC8 [CX1045]	CAT15004@SOIC8 [CX1045]
CAT15008@SOIC8 [CX1045]	CAT15016@SOIC8 [CX1045]

CAT1640 [CX0001]	CAT1640@SOIC8 [CX1045]
CAT1640@TDFN8 [CX0001]	CAT1640@TSSOP8 [CX1059]
CAT1641 [CX0001]	CAT1641@SOIC8 [CX1045]
CAT1641@TDFN8 [CX0001]	CAT1641@TSSOP8 [CX1059]
CAT24AA01@SOIC8 [CX1045]	CAT24AA01@TSOT-23 [CX1041]
CAT24AA02@SOIC8 [CX1045]	CAT24AA02@TSOT-23 [CX1041]
CAT24AA04@SOIC8 [CX1045]	CAT24AA04@TSOT-23 [CX1041]
CAT24AA08@SOIC8 [CX1045]	CAT24AA08@TSOT-23 [CX1041]
CAT24AA16@SOIC8 [CX1045]	CAT24AA16@TSOT-23 [CX1041]
CAT24C32 [CX0001]	CAT24C32@SOIC8 [CX1045]
CAT24C32@TDFN8 [CX4002]	CAT24C32@TSSOP8 [CX1059]
CAT24C32@UDFN8 [CX4002]	CAT34TS02@TDFN8 [CX0001]
CAT93C46R(08bit) [CX0001]	
CAT93C46R(08bit)(V)@SOIC8 [CX1045]	
CAT93C46R(08bit)(VP2)@TDFN8 [CX4002]	
CAT93C46R(08bit)(W)@SOIC8 [CX1045]	
CAT93C46R(08bit)(X)@SOIC8 [CX1045]	
CAT93C46R(08bit)(Y)@TSSOP8 [CX1059]	
CAT93C46R(16bit)(V)@SOIC8 [CX1045]	
CAT93C46R(16bit)(VP2)@TDFN8 [CX4002]	
CAT93C46R(16bit)(W)@SOIC8 [CX1045]	
CAT93C46R(16bit)(X)@SOIC8 [CX1045]	
CAT93C46R(16bit)(Y)@TSSOP8 [CX1059]	
CAT93C46R-16 [CX0001]	CAT93C56(08bit) [CX0001]
CAT93C56(08bit)@SOIC8(150mil) [CX1045]	
CAT93C56(08bit)@SOIC8(208mil) [CX1044]	
CAT93C56(08bit)@TDFN8(2*3) [CX4002]	
CAT93C56(08bit)@TDFN8(3*3) [CX4003]	
CAT93C56(08bit)@TSSOP8 [CX1059]	CAT93C56(16bit) [CX0001]
CAT93C56(16bit)@SOIC8(150mil) [CX1045]	
CAT93C56(16bit)@SOIC8(208mil) [CX1044]	
CAT93C56(16bit)@TDFN8(2*3) [CX4002]	
CAT93C56(16bit)@TDFN8(3*3) [CX4003]	
CAT93C56(16bit)@TSSOP8 [CX1059]	CAT93C57(08bit) [CX0001]
CAT93C57(08bit)@SOIC8(150mil) [CX1045]	
CAT93C57(08bit)@SOIC8(208mil) [CX1044]	
CAT93C57(08bit)@TDFN8(2*3) [CX4002]	
CAT93C57(08bit)@TDFN8(3*3) [CX4003]	
CAT93C57(08bit)@TSSOP8 [CX1059]	CAT93C57(16bit) [CX0001]
CAT93C57(16bit)@SOIC8(150mil) [CX1045]	
CAT93C57(16bit)@SOIC8(208mil) [CX1044]	
CAT93C57(16bit)@TDFN8(2*3) [CX4002]	
CAT93C57(16bit)@TDFN8(3*3) [CX4003]	
CAT93C57(16bit)@TSSOP8 [CX1059]	CAV24C02@SOIC8 [CX1045]
CAV24C02@TSSOP8 [CX1059]	CAV24C04@SOIC8 [CX1045]
CAV24C04@TSSOP8 [CX1059]	CAV24C08@SOIC8 [CX1045]
CAV24C08@TSSOP8 [CX1059]	CAV24C16@SOIC8 [CX1045]
CAV24C16@TSSOP8 [CX1059]	CAV24C32@SOIC8 [CX1045]
CAV24C32@TSSOP8 [CX1059]	CAV24C64@SOIC8 [CX1045]
CAV24C64@TSSOP8 [CX1059]	

## MICROCONTROLLER

LC87F2C64A@QFP80 [CX3018]	LC87F2C64A@TQFP80 [CX3016]
LC87F2J04A@QIP48E [CX3093]	LC87F2J04A@SQFP48 [CX3007]
LC87F2J08A@QIP48E [CX3093]	LC87F2J08A@SQFP48 [CX3007]
LC87F2J16A@QIP48E [CX3093]	LC87F2J16A@SQFP48 [CX3007]
LC87F2J32A@QIP48E [CX3093]	LC87F2J32A@SQFP48 [CX3007]
LC87F5G32A@QIP48E [CX3093]	LC87F5G32A@SQFP48 [CX3007]

LC87F5N62B@QIP100E [CX3022]

LC87F5VP6AU@QIP100E [CX3022]

## PANASONIC

### MICROCONTROLLER

MN103SFA7K@LQFP80 [CX3017]  
MN103SFC2DXW [CX3003]  
MN103SFJ9D [CX3003]

MN103SFC2D [CX3003]  
MN103SFH9G [CX3043]  
MN103SFJ9DXW [CX3003]

## PARALLAX

### MICROCONTROLLER

SX20AC/SS/G@SSOP20 [CX1026]  
SX28AC/DP [CX0001]  
SX28AC/SS/G@SSOP28 [CX1026]  
SX48BD/G@TQFP48 [CX3047]

SX20AC/SS@SSOP20 [CX1026]  
SX28AC/DP/G [CX0001]  
SX28AC/SS@SSOP28 [CX1026]  
SX48BD@TQFP48 [CX3047]

## PCT

### E (E) PROM/FRAM/NVRAM

PCT25LF010@SOIC8(4.0) [CX1045]  
PCT25LF010@WSON8 [CX4005]  
PCT25LF010A@SOIC8(5.4) [CX1044]  
PCT25LF016A@SOIC8(4.0) [CX1045#1]  
PCT25LF016A@SOIC8(5.4) [CX1044#1]  
PCT25LF016A@WSON8 [CX4005#1]  
PCT25LF016B@SOIC8(4.0) [CX1045#1]  
PCT25LF016B@SOIC8(5.4) [CX1044#1]  
PCT25LF016B@WSON8 [CX4005#1]  
PCT25LF020@SOIC8(5.4) [CX1044]  
PCT25LF020A@SOIC8(4.0) [CX1045]  
PCT25LF020A@WSON8 [CX4005]  
PCT25LF040@SOIC8(5.4) [CX1044]  
PCT25LF040A@SOIC8(4.0) [CX1045]  
PCT25LF040A@WSON8 [CX4005]  
PCT25LF080@SOIC8(5.4) [CX1044]  
PCT25LF080A@SOIC8(4.0) [CX1045]  
PCT25LF080A@WSON8 [CX4005]  
PCT25VF010@SOIC8(5.4) [CX1044]  
PCT25VF010A@SOIC8(4.0) [CX1045]  
PCT25VF010A@WSON8 [CX4005]  
PCT25VF016B@SOIC8(4.0) [CX1045#1]  
PCT25VF016B@SOIC8(5.4) [CX1044#1]  
PCT25VF016B@WSON8 [CX4005#1]  
PCT25VF020@SOIC8(5.4) [CX1044]  
PCT25VF020B@SOIC8(4.0) [CX1045#1]  
PCT25VF020B@SOIC8(5.4) [CX1044#1]  
PCT25VF020B@WSON8 [CX4005#1]  
PCT25VF032B@SOIC8(4.0) [CX1045#1]  
PCT25VF032B@SOIC8(5.4) [CX1044#1]  
PCT25VF032B@WSON8 [CX4005#1]  
PCT25VF040@SOIC8(5.4) [CX1044]  
PCT25VF040B@SOIC8(4.0) [CX1045#1]

PCT25LF010@SOIC8(5.4) [CX1044]  
PCT25LF010A@SOIC8(4.0) [CX1045]  
PCT25LF010A@WSON8 [CX4005]  
  
PCT25LF020@SOIC8(4.0) [CX1045]  
PCT25LF020@WSON8 [CX4005]  
PCT25LF020A@SOIC8(5.4) [CX1044]  
PCT25LF040@SOIC8(4.0) [CX1045]  
PCT25LF040@WSON8 [CX4005]  
PCT25LF040A@SOIC8(5.4) [CX1044]  
PCT25LF080@SOIC8(4.0) [CX1045]  
PCT25LF080@WSON8 [CX4005]  
PCT25LF080A@SOIC8(5.4) [CX1044]  
PCT25VF010@SOIC8(4.0) [CX1045]  
PCT25VF010@WSON8 [CX4005]  
PCT25VF010A@SOIC8(5.4) [CX1044]  
  
PCT25VF020@SOIC8(4.0) [CX1045]  
PCT25VF020@WSON8 [CX4005]  
  
PCT25VF032B@SOIC16 [CX1033#1]  
  
PCT25VF040@SOIC8(4.0) [CX1045]  
PCT25VF040@WSON8 [CX4005]

PCT25VF040B@SOIC8(5.4) [CX1044#1]  
PCT25VF040B@WSON8 [CX4005#1]  
PCT25VF080@SOIC8(5.4) [CX1044]  
PCT25VF080B@SOIC8(4.0) [CX1045#1]  
PCT25VF080B@SOIC8(5.4) [CX1044#1]  
PCT25VF080B@WSON8 [CX4005#1]  
PCT25VF512@SOIC8(5.4) [CX1044]  
PCT25VF512A@SOIC8(4.0) [CX1045]  
PCT25VF512A@WSON8 [CX4005]  
PCT25WF010@SOIC8(5.4) [CX1044]  
PCT25WF020@SOIC8(4.0) [CX1045]  
PCT25WF020@WSON8 [CX4005]  
PCT25WF040@SOIC8(5.4) [CX1044]  
PCT25WF080@SOIC8(4.0) [CX1045]  
PCT25WF080@WSON8 [CX4005]  
PCT25WF512@SOIC8(5.4) [CX1044]  
PCT25VF080@SOIC8(4.0) [CX1045]  
PCT25VF080@WSON8 [CX4005]  
PCT25VF512@SOIC8(4.0) [CX1045]  
PCT25VF512@WSON8 [CX4005]  
PCT25VF512A@SOIC8(5.4) [CX1044]  
PCT25WF010@SOIC8(4.0) [CX1045]  
PCT25WF010@WSON8 [CX4005]  
PCT25WF020@SOIC8(5.4) [CX1044]  
PCT25WF040@SOIC8(4.0) [CX1045]  
PCT25WF040@WSON8 [CX4005]  
PCT25WF080@SOIC8(5.4) [CX1044]  
PCT25WF512@SOIC8(4.0) [CX1045]  
PCT25WF512@WSON8 [CX4005]

## PHILIPS

### E (E) PROM/FRAM/NVRAM

27C010 [CX0001]  
27C010@TSOP32 [CX1002]  
27C040@PLCC32 [CX2032]  
27C210 [CX0001]  
27C240 [CX0001]  
27C256 [CX0001]  
27C32 [CX0001]  
27C512@PLCC32  
27C64@PLCC32 [CX2032]  
27C64A@PLCC32 [CX2032]  
27C64AF@PLCC32 [CX2032]  
27HC641@PLCC28  
PCA24S08@SOIC8 [CX1045]  
PCA8574(P) [CX0001]  
PCA8574(TS)@SSOP20 [CX1000]  
PCA8574A(T)@SOIC16 [CX1033]  
PCA8581 [CX0001]  
PCA8581C [CX0001]  
PCA8582A [CX0001]  
PCA8582B [CX0001]  
PCA8582C [CX0001]  
PCA8582D [CX0001]  
PCA8582E [CX0001]  
PCA9500@HQVFN16 [CX4009]  
PCA9500@TSSOP16 [CX1000]  
PCA9501@SOIC20 [CX1033]  
PCD8581 [CX0001]  
PCD8581C [CX0001]  
PCD8582A [CX0001]  
PCD8582B [CX0001]  
PCD8582C [CX0001]  
PCD8582D [CX0001]  
PCD8582E [CX0001]  
PCF85102C [CX0001]  
PCF85103C [CX0001]  
PCF85116 [CX0001]  
PCF8581 [CX0001]  
27C010@PLCC32 [CX2032]  
27C040 [CX0001]  
27C040@TSOP32 [CX1002]  
27C210@PLCC44 [CX2044]  
27C240@PLCC44 [CX2044]  
27C256@PLCC32  
27C512 [CX0001]  
27C64 [CX0001]  
27C64A [CX0001]  
27C64AF [CX0001]  
27HC641 [CX0001]  
27PC32 [CX0001]  
PCA24S08@TSSOP8 [CX1000]  
PCA8574(T)@SOIC16 [CX1033]  
PCA8574A(P) [CX0001]  
PCA8574A(TS)@SSOP20 [CX1000]  
PCA8581@SOIC8 [CX1045]  
PCA8581C@SOIC8 [CX1045]  
PCA8582A@SOIC8 [CX1045]  
PCA8582B@SOIC8 [CX1045]  
PCA8582C@SOIC8 [CX1045]  
PCA8582D@SOIC8 [CX1045]  
PCA8582E@SOIC8 [CX1045]  
PCA9500@SOIC16 [CX1033]  
PCA9501@HQVFN20  
PCA9501@TSSOP20 [CX1000]  
PCD8581@SOIC8 [CX1045]  
PCD8581C@SOIC8 [CX1045]  
PCD8582A@SOIC8 [CX1045]  
PCD8582B@SOIC8 [CX1045]  
PCD8582C@SOIC8 [CX1045]  
PCD8582D@SOIC8 [CX1045]  
PCD8582E@SOIC8 [CX1045]  
PCF85102C@SOIC8 [CX1045]  
PCF85103C@SOIC8 [CX1045]  
PCF85116@SOIC8 [CX1045]  
PCF8581@SOIC8 [CX1045]

PCF8581C [CX0001]  
PCF8582A [CX0001]  
PCF8582B [CX0001]  
PCF8582C [CX0001]  
PCF8582D [CX0001]  
PCF8582E [CX0001]  
PCF8594 [CX0001]  
PCF8594C [CX0001]  
PCF8594D [CX0001]  
PCF8594E [CX0001]  
PCF8598 [CX0001]  
PCF8598C [CX0001]  
PCF8598D [CX0001]  
PCF8598E [CX0001]

PCF8581C@SOIC8 [CX1045]  
PCF8582A@SOIC8 [CX1045]  
PCF8582B@SOIC8 [CX1045]  
PCF8582C@SOIC8 [CX1045]  
PCF8582D@SOIC8 [CX1045]  
PCF8582E@SOIC8 [CX1045]  
PCF8594@SOIC8 [CX1045]  
PCF8594C@SOIC8 [CX1045]  
PCF8594D@SOIC8 [CX1045]  
PCF8594E@SOIC8 [CX1045]  
PCF8598@SOIC8 [CX1044]  
PCF8598C@SOIC8 [CX1044]  
PCF8598D@SOIC8 [CX1044]  
PCF8598E@SOIC8 [CX1044]

## BPROM

82S126 [CX0001]  
82S129 [CX0001]  
82S130 [CX0001]  
82S131 [CX0001]  
82S140 [CX0001]  
N82LS135 [CX0001]  
N82S123 [CX0001]  
N82S135 [CX0001]  
N82S136 [CX0001]  
N82S137A [CX0001]  
N82S137C [CX0001]  
N82S146@PLCC20 [CX2020]  
N82S147@PLCC20 [CX2020]  
N82S147A@PLCC20 [CX2020]  
N82S147B@PLCC20 [CX2020]  
N82S23 [CX0001]

82S126A [CX0001]  
82S129A [CX0001]  
82S130A [CX0001]  
82S131A [CX0001]  
82S141 [CX0001]  
N82LS135@PLCC20 [CX2020]  
N82S123A [CX0001]  
N82S135@PLCC20 [CX2020]  
N82S137 [CX0001]  
N82S137B [CX0001]  
N82S146 [CX0001]  
N82S147 [CX0001]  
N82S147A [CX0001]  
N82S147B [CX0001]  
N82S167 [CX0001]  
N82S23A [CX0001]

## PLD

82S105 [CX0001]  
82S152 [CX0001]  
82S153 [CX0001]  
82S155 [CX0001]  
82S157 [CX0001]  
82S159 [CX0001]  
82S167 [CX0001]  
82S168 [CX0001]  
82S173 [CX0001]  
82S179 [CX0001]  
PLC18V8Z [CX0001]  
PLC18V8ZI [CX0001]  
PLS104 [CX0001]  
PLS104A [CX0001]  
PLS105 [CX0001]  
PLS105A [CX0001]  
PLS152 [CX0001]  
PLS153 [CX0001]  
PLS153A [CX0001]  
PLS155 [CX0001]  
PLS157 [CX0001]  
PLS159 [CX0001]

82S105@PLCC28 [CX2028]  
82S152@PLCC20 [CX2020]  
82S153@PLCC20 [CX2020]  
82S155@PLCC20 [CX2020]  
82S157@PLCC20 [CX2020]  
82S159@PLCC20 [CX2020]  
82S167@PLCC28 [CX2028]  
82S168@PLCC28 [CX2028]  
82S173@PLCC28 [CX2028]  
82S179@PLCC28 [CX2028]  
PLC18V8Z@PLCC20 [CX2020]  
PLC18V8ZI@PLCC20 [CX2020]  
PLS104@PLCC28 [CX2028]  
PLS104A@PLCC28 [CX2028]  
PLS105@PLCC28 [CX2028]  
PLS105A@PLCC28 [CX2028]  
PLS152@PLCC20 [CX2020]  
PLS153@PLCC20 [CX2020]  
PLS153A@PLCC20 [CX2020]  
PLS155@PLCC20 [CX2020]  
PLS157@PLCC20 [CX2020]  
PLS159@PLCC20 [CX2020]

PLS159A [CX0001]  
PLS167 [CX0001]  
PLS167A [CX0001]  
PLS168 [CX0001]  
PLS168A [CX0001]  
PLS173 [CX0001]  
PLS179 [CX0001]  
PZ3032@PLCC44 [CX2044]  
PZ3032CS@PLCC44 [CX2044]

PLS159A@PLCC20 [CX0001]  
PLS167@PLCC28 [CX2028]  
PLS167A@PLCC28 [CX2028]  
PLS168@PLCC28 [CX2028]  
PLS168A@PLCC28 [CX2028]  
PLS173@PLCC28 [CX2028]  
PLS179@PLCC28 [CX2028]  
PZ3032@TQFP44 [CX3003]  
PZ3032CS@TQFP44 [CX3003]

## MICROCONTROLLER

LPC1111/101@LQFP48 [CX3007]  
LPC1111/101@QFP44 [CX3005]  
LPC1111/102@QFN33 [CX4016]  
LPC1111/103@LQFP48 [CX3007]  
LPC1111/103@QFP44 [CX3005]  
LPC1111/201@QFN33 [CX4016]  
LPC1111/202@LQFP48 [CX3007]  
LPC1111/202@QFP44 [CX3005]  
LPC1111/203@QFN33 [CX4016]  
LPC1111@LQFP48 [CX3007]  
LPC1111@QFP44 [CX3005]  
LPC1112/101@QFN33 [CX4016]  
LPC1112/102@LQFP48 [CX3007]  
LPC1112/102@QFP44 [CX3005]  
LPC1112/103@QFN33 [CX4016]  
LPC1112/201@LQFP48 [CX3007]  
LPC1112/201@QFP44 [CX3005]  
LPC1112/202@QFN33 [CX4016]  
LPC1112/203@LQFP48 [CX3007]  
LPC1112/203@QFP44 [CX3005]  
LPC1112@QFN33 [CX4016]  
LPC1113/101@LQFP48 [CX3007]  
LPC1113/101@QFP44 [CX3005]  
LPC1113/102@QFN33 [CX4016]  
LPC1113/103@LQFP48 [CX3007]  
LPC1113/103@QFP44 [CX3005]  
LPC1113/201@QFN33 [CX4016]  
LPC1113/202@LQFP48 [CX3007]  
LPC1113/202@QFP44 [CX3005]  
LPC1113/203@QFN33 [CX4016]  
LPC1113/301@QFN33 [CX4016]  
LPC1113/301@QFP48 [CX3007]  
LPC1113/302@QFP44 [CX3005]  
LPC1113/303@QFN33 [CX4016]  
LPC1113/303@QFP48 [CX3007]  
LPC1113@QFN33 [CX4016]  
LPC1114/101@LQFP48 [CX3007]  
LPC1114/101@QFP44 [CX3005]  
LPC1114/102@QFN33 [CX4016]  
LPC1114/103@LQFP48 [CX3007]  
LPC1114/103@QFP44 [CX3005]  
LPC1114/201@QFN33 [CX4016]  
LPC1114/202@LQFP48 [CX3007]  
LPC1114/202@QFP44 [CX3005]  
LPC1114/203@QFN33 [CX4016]  
LPC1114/301@QFN33 [CX4016]  
LPC1114/301@QFP48 [CX3007]

LPC1111/101@QFN33 [CX4016]  
LPC1111/102@LQFP48 [CX3007]  
LPC1111/102@QFP44 [CX3005]  
LPC1111/103@QFN33 [CX4016]  
LPC1111/201@LQFP48 [CX3007]  
LPC1111/201@QFP44 [CX3005]  
LPC1111/202@QFN33 [CX4016]  
LPC1111/203@LQFP48 [CX3007]  
LPC1111/203@QFP44 [CX3005]  
LPC1111@QFN33 [CX4016]  
LPC1112/101@LQFP48 [CX3007]  
LPC1112/101@QFP44 [CX3005]  
LPC1112/102@QFN33 [CX4016]  
LPC1112/103@LQFP48 [CX3007]  
LPC1112/103@QFP44 [CX3005]  
LPC1112/201@QFN33 [CX4016]  
LPC1112/202@LQFP48 [CX3007]  
LPC1112/202@QFP44 [CX3005]  
LPC1112/203@QFN33 [CX4016]  
LPC1112@LQFP48 [CX3007]  
LPC1112@QFP44 [CX3005]  
LPC1113/101@QFN33 [CX4016]  
LPC1113/102@LQFP48 [CX3007]  
LPC1113/102@QFP44 [CX3005]  
LPC1113/103@QFN33 [CX4016]  
LPC1113/201@LQFP48 [CX3007]  
LPC1113/201@QFP44 [CX3005]  
LPC1113/202@QFN33 [CX4016]  
LPC1113/203@LQFP48 [CX3007]  
LPC1113/203@QFP44 [CX3005]  
LPC1113/301@QFP44 [CX3005]  
LPC1113/302@QFN33 [CX4016]  
LPC1113/302@QFP48 [CX3007]  
LPC1113/303@QFP44 [CX3005]  
LPC1113@LQFP48 [CX3007]  
LPC1113@QFP44 [CX3005]  
LPC1114/101@QFN33 [CX4016]  
LPC1114/102@LQFP48 [CX3007]  
LPC1114/102@QFP44 [CX3005]  
LPC1114/103@QFN33 [CX4016]  
LPC1114/201@LQFP48 [CX3007]  
LPC1114/201@QFP44 [CX3005]  
LPC1114/202@QFN33 [CX4016]  
LPC1114/203@LQFP48 [CX3007]  
LPC1114/203@QFP44 [CX3005]  
LPC1114/301@QFP44 [CX3005]  
LPC1114/302@QFN33 [CX4016]

LPC1114/302@QFP44 [CX3005]  
LPC1114/303@QFN33 [CX4016]  
LPC1114/303@QFP48 [CX3007]  
LPC1114/323@QFP44 [CX3005]  
LPC1114/333@QFN33 [CX4016]  
LPC1114/333@QFP48 [CX3007]  
LPC1114@QFN33 [CX4016]  
LPC1115/303@QFP48 [CX3007]  
LPC11A11/001@QFP48 [CX3007]  
LPC11A12/101@QFP48 [CX3007]  
LPC11A13/201@QFP48 [CX3007]  
LPC11A14/301@QFP48 [CX3007]  
LPC11C12/102@LQFP48 [CX3007]  
LPC11C12/201@LQFP48 [CX3007]  
LPC11C12/203@LQFP48 [CX3007]  
LPC11C12@LQFP48 [CX3007]  
LPC11C14/102@LQFP48 [CX3007]  
LPC11C14/201@LQFP48 [CX3007]  
LPC11C14/203@LQFP48 [CX3007]  
LPC11C14@LQFP48 [CX3007]  
LPC11C22/102@LQFP48 [CX3007]  
LPC11C22/201@LQFP48 [CX3007]  
LPC11C22/203@LQFP48 [CX3007]  
LPC11C22@LQFP48 [CX3007]  
LPC11C24/102@LQFP48 [CX3007]  
LPC11C24/201@LQFP48 [CX3007]  
LPC11C24/203@LQFP48 [CX3007]  
LPC11C24@LQFP48 [CX3007]  
LPC11U33@QFN33 [CX4016]  
LPC11U34/421@QFN33 [CX4016]  
LPC11U35/301@QFP48 [CX3007]  
LPC11U35/401@BGA48 [BBBB]  
LPC11U35/401@QFP64 [CX3011]  
LPC11U35/501@QFP48 [CX3007]  
LPC11U36/301@BGA48 [BBBB]  
LPC11U36/301@QFP64 [CX3011]  
LPC11U36/401@QFP48 [CX3007]  
LPC11U36/501@BGA48 [BBBB]  
LPC11U36/501@QFP64 [CX3011]  
LPC11U37/301@QFP48 [CX3007]  
LPC11U37/401@BGA48 [BBBB]  
LPC11U37/401@QFP64 [CX3011]  
LPC11U37/501@QFP48 [CX3007]  
LPC1224/101@LQFP48 [CX3007]  
LPC1224/121@LQFP48 [CX3007]  
LPC1224/201@LQFP48 [CX3007]  
LPC1224/221@LQFP48 [CX3007]  
LPC1225/201@LQFP48 [CX3007]  
LPC1225/221@LQFP48 [CX3007]  
LPC1225/301@LQFP48 [CX3007]  
LPC1225/321@LQFP48 [CX3007]  
LPC1226/201@LQFP48 [CX3007]  
LPC1226/301@LQFP48 [CX3007]  
LPC1227/201@LQFP48 [CX3007]  
LPC1227/301@LQFP48 [CX3007]  
LPC12D27/201@LQFP100 [CX3043]  
LPC12D27/201@LQFP64 [CX3011]  
LPC12D27/301@LQFP48 [CX3007]  
LPC1311@LQFP48 [CX3007]  
LPC1114/302@QFP48 [CX3007]  
LPC1114/303@QFP44 [CX3005]  
LPC1114/323@QFN33 [CX4016]  
LPC1114/323@QFP48 [CX3007]  
LPC1114/333@QFP44 [CX3005]  
LPC1114@LQFP48 [CX3007]  
LPC1114@QFP44 [CX3005]  
LPC11A11/001@QFN33 [CX4016]  
LPC11A12/101@QFN33 [CX4016]  
LPC11A13/201@QFN33 [CX4016]  
LPC11A14/301@QFN33 [CX4016]  
LPC11C12/101@LQFP48 [CX3007]  
LPC11C12/103@LQFP48 [CX3007]  
LPC11C12/202@LQFP48 [CX3007]  
LPC11C12/301@LQFP48 [CX3007]  
LPC11C14/101@LQFP48 [CX3007]  
LPC11C14/103@LQFP48 [CX3007]  
LPC11C14/202@LQFP48 [CX3007]  
LPC11C14/301@LQFP48 [CX3007]  
LPC11C22/101@LQFP48 [CX3007]  
LPC11C22/103@LQFP48 [CX3007]  
LPC11C22/202@LQFP48 [CX3007]  
LPC11C22/301@LQFP48 [CX3007]  
LPC11C24/101@LQFP48 [CX3007]  
LPC11C24/103@LQFP48 [CX3007]  
LPC11C24/202@LQFP48 [CX3007]  
LPC11C24/301@LQFP48 [CX3007]  
LPC11D14FBD100 [CX3043]  
LPC11U34/311@QFN33 [CX4016]  
LPC11U35/301@BGA48 [BBBB]  
LPC11U35/301@QFP64 [CX3011]  
LPC11U35/401@QFP48 [CX3007]  
LPC11U35/501@BGA48 [BBBB]  
LPC11U35/501@QFP64 [CX3011]  
LPC11U36/301@QFP48 [CX3007]  
LPC11U36/401@BGA48 [BBBB]  
LPC11U36/401@QFP64 [CX3011]  
LPC11U36/501@QFP48 [CX3007]  
LPC11U37/301@BGA48 [BBBB]  
LPC11U37/301@QFP64 [CX3011]  
LPC11U37/401@QFP48 [CX3007]  
LPC11U37/501@BGA48 [BBBB]  
LPC11U37/501@QFP64 [CX3011]  
LPC1224/101@LQFP64 [CX3011]  
LPC1224/121@LQFP64 [CX3011]  
LPC1224/201@LQFP64 [CX3011]  
LPC1224/221@LQFP64 [CX3011]  
LPC1225/201@LQFP64 [CX3011]  
LPC1225/221@LQFP64 [CX3011]  
LPC1225/301@LQFP64 [CX3011]  
LPC1225/321@LQFP64 [CX3011]  
LPC1226/201@LQFP64 [CX3011]  
LPC1226/301@LQFP64 [CX3011]  
LPC1227/201@LQFP64 [CX3011]  
LPC1227/301@LQFP64 [CX3011]  
LPC12D27/201@LQFP48 [CX3007]  
LPC12D27/301@LQFP100 [CX3043]  
LPC12D27/301@LQFP64 [CX3011]  
LPC1311@QFN33 [CX4016]



LPC1312@LQFP48 [CX3007]                   LPC1312@QFN33 [CX4016]  
LPC1313@LQFP48 [CX3007]                   LPC1313@QFN33 [CX4016]  
LPC1314@LQFP48 [CX3007]                   LPC1314@QFN33 [CX4016]  
LPC1341@LQFP48 [CX3007]                   LPC1341@QFN33 [CX4016]  
LPC1342@LQFP48 [CX3007]                   LPC1342@QFN33 [CX4016]  
LPC1343@LQFP48 [CX3007]                   LPC1343@QFN33 [CX4016]  
LPC1344@LQFP48 [CX3007]                   LPC1344@QFN33 [CX4016]  
LPC1751@LQFP80 [CX3016]                   LPC1752@LQFP80 [CX3016]  
LPC1754@LQFP80 [CX3016]                   LPC1756@LQFP80 [CX3016]  
LPC1758@LQFP80 [CX3016]                   LPC1759@LQFP80 [CX3016]  
LPC1763@LQFP100 [CX3043]                   LPC1763FET100 [CX5055]  
LPC1764@LQFP100 [CX3043]                   LPC1764FET100 [CX5055]  
LPC1765@LQFP100 [CX3043]                   LPC1765FET100 [CX5055]  
LPC1766@LQFP100 [CX3043]                   LPC1766FET100 [CX5055]  
LPC1767@LQFP100 [CX3043]                   LPC1767FET100 [CX5055]  
LPC1768@LQFP100 [CX3043]                   LPC1768FET100 [CX5055]  
LPC1769@LQFP100 [CX3043]                   LPC1769FET100 [CX5055]  
LPC2101FBD48/00@LQFP48 [CX3007]           LPC2101FBD48/01@LQFP48 [CX3007]  
LPC2101FBD48@LQFP48 [CX3007]           LPC2101FHN48/00@HVQFN48 [CX4021]  
LPC2101FHN48/01@HVQFN48 [CX4021]       LPC2101FHN48@HVQFN48 [CX4021]  
LPC2102FBD48/00@LQFP48 [CX3007]       LPC2102FBD48/01@LQFP48 [CX3007]  
LPC2102FBD48@LQFP48 [CX3007]       LPC2102FHN48/00@HVQFN48 [CX4021]  
LPC2102FHN48/01@HVQFN48 [CX4021]       LPC2102FHN48@HVQFN48 [CX4021]  
LPC2103FA44@PLCC44 [CX2144]              LPC2103FBD48/00@LQFP48 [CX3007]  
LPC2103FBD48/01@LQFP48 [CX3007]       LPC2103FBD48@LQFP48 [CX3007]  
LPC2103FHN48/00@HVQFN48 [CX4021]       LPC2103FHN48/01@HVQFN48 [CX4021]  
LPC2103FHN48@HVQFN48 [CX4021]       LPC2104BBD48@LQFP48 [CX3007]  
LPC2104FBD48/00@LQFP48 [CX3007]       LPC2104FBD48/01@LQFP48 [CX3007]  
LPC2104FBD48@LQFP48 [CX3007]       LPC2104FHN48/00@HVQFN48 [CX4021]  
LPC2104FHN48/01@HVQFN48 [CX4021]       LPC2104FHN48@HVQFN48 [CX4021]  
LPC2105BBD48@LQFP48 [CX3007]           LPC2105FBD48/00@LQFP48 [CX3007]  
LPC2105FBD48/01@LQFP48 [CX3007]       LPC2105FBD48@LQFP48 [CX3007]  
LPC2105FHN48/00@HVQFN48 [CX4021]       LPC2105FHN48/01@HVQFN48 [CX4021]  
LPC2105FHN48@HVQFN48 [CX4021]       LPC2106BBD48@LQFP48 [CX3007]  
LPC2106FBD48/00@LQFP48 [CX3007]       LPC2106FBD48/01@LQFP48 [CX3007]  
LPC2106FBD48@LQFP48 [CX3007]       LPC2106FHN48/00@HVQFN48 [CX4021]  
LPC2106FHN48/01@HVQFN48 [CX4021]       LPC2106FHN48@HVQFN48 [CX4021]  
LPC2131FBD64@LQFP64 [CX3011]           LPC2131FHN64@QFN64 [CX4023]  
LPC2132FBD64@LQFP64 [CX3011]           LPC2132FHN64@QFN64 [CX4023]  
LPC2134FBD64@LQFP64 [CX3011]           LPC2134FHN64@QFN64 [CX4023]  
LPC2136FBD64@LQFP64 [CX3011]           LPC2136FHN64@QFN64 [CX4023]  
LPC2138FBD64@LQFP64 [CX3011]           LPC2138FHN64@QFN64 [CX4023]  
P83C660X2@PLCC44 [CX2044]              P83C660X2@TQFP44 [CX3005]  
P83C661X2@PLCC44 [CX2044]              P83C661X2@TQFP44 [CX3005]  
P87C054@SDIP42 [CX0042]               P87C055@SDIP42 [CX0042]  
P87C51 [CX0001]                       P87C51@PLCC44 [CX2044]  
P87C51@TQFP44 [CX3002]               P87C51FA [CX0001]  
P87C51FA@PLCC44 [CX2044]              P87C51FA@TQFP44 [CX3002]  
P87C51FB [CX0001]                      P87C51FB@PLCC44 [CX2044]  
P87C51FB@TQFP44 [CX3002]              P87C51FC [CX0001]  
P87C51FC@PLCC44 [CX2044]              P87C51FC@TQFP44 [CX3003]  
P87C51MA2@PLCC44 [CX2044]           P87C51MB2@PLCC44 [CX2044]  
P87C51MC2@PLCC44 [CX2044]           P87C51RA+ [CX0001]  
P87C51RA+@PLCC44 [CX2044]           P87C51RA+@TQFP44 [CX3003]  
P87C51RA2 [CX0001]                   P87C51RA2@PLCC44 [CX2044]  
P87C51RA2@TQFP44 [CX3002]           P87C51RB+ [CX0001]  
P87C51RB+@PLCC44 [CX2044]           P87C51RB+@TQFP44 [CX3003]  
P87C51RB2 [CX0001]                   P87C51RB2@PLCC44 [CX2044]  
P87C51RB2@TQFP44 [CX3002]           P87C51RC+ [CX0001]

P87C51RC+@PLCC44 [CX2044]  
P87C51RC2 [CX0001]  
P87C51RC2@TQFP44 [CX3002]  
P87C51RD+@PLCC44 [CX2044]  
P87C51RD2 [CX0001]  
P87C51RD2@TQFP44 [CX3002]  
P87C51SB@PLCC44 [CX2044]  
P87C51SF [CX0001]  
P87C51SF@TQFP44 [CX3002]  
P87C51UB@PLCC44 [CX2044]  
P87C51UF [CX0001]  
P87C51UF@TQFP44 [CX3002]  
P87C51X2@PLCC44 [CX2044]  
P87C51X2@TTSOP38 [CX1049]  
P87C52@PLCC44 [CX2044]  
P87C524 [CX0001]  
P87C524@TQFP44 [CX3003]  
P87C528@PLCC44 [CX2044]  
P87C52SB [CX0001]  
P87C52SB@TQFP44 [CX3002]  
P87C52SF@PLCC44 [CX2044]  
P87C52UB [CX0001]  
P87C52UB@TQFP44 [CX3002]  
P87C52UF@PLCC44 [CX2044]  
P87C52X2 [CX0001]  
P87C52X2@TQFP44 [CX3005]  
P87C54 [CX0001]  
P87C54@TQFP44 [CX3002]  
P87C54SB@PLCC44 [CX2044]  
P87C54SF [CX0001]  
P87C54SF@TQFP44 [CX3002]  
P87C54UB@PLCC44 [CX2044]  
P87C54UF [CX0001]  
P87C54UF@TQFP44 [CX3002]  
P87C54X2@PLCC44 [CX2044]  
P87C54X2@TTSOP38 [CX1049]  
P87C550@PLCC44 [CX2044]  
P87C575@PLCC44 [CX2044]  
P87C576 [CX0001]  
P87C576@TQFP44 [CX3002]  
P87C58@PLCC44 [CX2044]  
P87C58SB [CX0001]  
P87C58SB@TQFP44 [CX3002]  
P87C58UB@PLCC44 [CX2044]  
P87C58X2 [CX0001]  
P87C58X2@TQFP44 [CX3005]  
P87C591@PLCC44 [CX2044]  
P87C652 [CX0001]  
P87C652@TQFP44 [CX3002]  
P87C654@PLCC44 [CX2044]  
P87C660X2@PLCC44 [CX2044]  
P87C661X2@PLCC44 [CX2044]  
P87C748 [CX0001]  
P87C749 [CX0001]  
P87C750 [CX0001]  
P87C750@SSOP24 [CX1026]  
P87C751@PLCC28 [CX2028]  
P87C752 [CX0001]  
P87C752@SSOP28 [CX1026]

P87C51RC+@TQFP44 [CX3003]  
P87C51RC2@PLCC44 [CX2044]  
P87C51RD+ [CX0001]  
P87C51RD+@TQFP44 [CX3003]  
P87C51RD2@PLCC44 [CX2044]  
P87C51SB [CX0001]  
P87C51SB@TQFP44 [CX3002]  
P87C51SF@PLCC44 [CX2044]  
P87C51UB [CX0001]  
P87C51UB@TQFP44 [CX3002]  
P87C51UF@PLCC44 [CX2044]  
P87C51X2 [CX0001]  
P87C51X2@TQFP44 [CX3005]  
P87C52 [CX0001]  
P87C52@TQFP44 [CX3002]  
P87C524@PLCC44 [CX2044]  
P87C528 [CX0001]  
P87C528@TQFP44 [CX3003]  
P87C52SB@PLCC44 [CX2044]  
P87C52SF [CX0001]  
P87C52SF@TQFP44 [CX3002]  
P87C52UB@PLCC44 [CX2044]  
P87C52UF [CX0001]  
P87C52UF@TQFP44 [CX3002]  
P87C52X2@PLCC44 [CX2044]  
P87C52X2@TTSOP38 [CX1049]  
P87C54@PLCC44 [CX2044]  
P87C54SB [CX0001]  
P87C54SB@TQFP44 [CX3002]  
P87C54SF@PLCC44 [CX2044]  
P87C54UB [CX0001]  
P87C54UB@TQFP44 [CX3002]  
P87C54UF@PLCC44 [CX2044]  
P87C54X2 [CX0001]  
P87C54X2@TQFP44 [CX3005]  
P87C550 [CX0001]  
P87C575 [CX0001]  
P87C575@TQFP44 [CX3002]  
P87C576@PLCC44 [CX2044]  
P87C58 [CX0001]  
P87C58@TQFP44 [CX3002]  
P87C58SB@PLCC44 [CX2044]  
P87C58UB [CX0001]  
P87C58UB@TQFP44 [CX3002]  
P87C58X2@PLCC44 [CX2044]  
P87C58X2@TTSOP38 [CX1049]  
P87C591@TQFP44 [CX3002]  
P87C652@PLCC44 [CX2044]  
P87C654 [CX0001]  
P87C654@TQFP44 [CX3002]  
P87C660X2@TQFP44 [CX3005]  
P87C661X2@TQFP44 [CX3005]  
P87C748@PLCC28 [CX2028]  
P87C749@PLCC28 [CX2028]  
P87C750@PLCC28 [CX2028]  
P87C751 [CX0001]  
P87C751@SSOP24 [CX1026]  
P87C752@PLCC28 [CX2028]  
P87C754 [CX0001]

P87C754@PLCC28 [CX2028]  
P87CL52X2 [CX0001]  
P87CL52X2@TQFP44 [CX3005]  
P87CL54X2 [CX0001]  
P87CL54X2@TQFP44 [CX3005]  
P87L51FA [CX0001]  
P87L51FA@TQFP44 [CX3002]  
P87L51FB@PLCC44 [CX2044]  
P87LPC759 [CX0001]  
P87LPC760 [CX0001]  
P87LPC760@TSSOP14 [CX1000]  
P87LPC761 [CX0001]  
P87LPC762 [CX0001]  
P87LPC762@PLCC44 [CX1044]  
P87LPC762@SOIC20 [CX1033]  
P87LPC764 [CX0001]  
P87LPC764@PLCC44 [CX1044]  
P87LPC764@SOIC20 [CX1033]  
P87LPC764@TSSOP20 [CX1001]  
P87LPC767 [CX0001]  
P87LPC767@PLCC44 [CX1044]  
P87LPC767@SOIC20 [CX1033]  
P87LPC768 [CX0001]  
P87LPC768@SOIC20 [CX1033]  
P87LPC769 [CX0001]  
P87LPC769@PLCC44 [CX1044]  
P87LPC769@SOIC20 [CX1033]  
P87LPC778 [CX0001]  
P87LPC778@TSSOP20 [CX1000]  
P87LPC779 [CX0001]  
P87LPC779@TSSOP20 [CX1000]  
P89C138 [CX0001]  
P89C138@TQFP44 [CX3005]  
P89C238@PLCC44 [CX2044]  
P89C51B [CX0001]  
P89C51B@TQFP44 [CX3005]  
P89C51RA+@PLCC44 [CX2044]  
P89C51RA2B [CX0001]  
P89C51RA2B@TQFP44 [CX3005]  
P89C51RB+@PLCC44 [CX2044]  
P89C51RB2B [CX0001]  
P89C51RB2B@TQFP44 [CX3005]  
P89C51RB2H@PLCC44 [CX2044]  
P89C51RC+ [CX0001]  
P89C51RC+@TQFP44 [CX3005]  
P89C51RC2B@PLCC44 [CX2044]  
P89C51RC2H [CX0001]  
P89C51RC2H@TQFP44 [CX3002]  
P89C51RD+@PLCC44 [CX2044]  
P89C51RD2B [CX0001]  
P89C51RD2B@TQFP44 [CX3005]  
P89C51RD2H@PLCC44 [CX2044]  
P89C51UB [CX0001]  
P89C51UB@TQFP44 [CX3005]  
P89C51UF@PLCC44 [CX2044]  
P89C51X2 [CX0001]  
P89C51X2@TQFP44 [CX3005]  
P89C51X2B@PLCC44 [CX2044]  
P89C51X2F [CX0001]

P87C754@SSOP28 [CX1026]  
P87CL52X2@PLCC44 [CX2044]  
P87CL52X2@TTSOP38 [CX1049]  
P87CL54X2@PLCC44 [CX2044]  
P87CL54X2@TTSOP38 [CX1049]  
P87L51FA@PLCC44 [CX2044]  
P87L51FB [CX0001]  
P87L51FB@TQFP44 [CX3002]  
P87LPC759(ISP) [CX0001]  
P87LPC760(ISP) [CX0001]  
P87LPC760@TSSOP14(ISP) [CX0001]  
P87LPC761(ISP) [CX0001]  
P87LPC762(ISP) [CX0001]  
P87LPC762@PLCC44(ISP) [CX0001]  
P87LPC762@SOIC20(ISP) [CX0001]  
P87LPC764(ISP) [CX0001]  
P87LPC764@PLCC44(ISP) [CX0001]  
P87LPC764@SOIC20(ISP) [CX0001]  
P87LPC764@TSSOP20(ISP) [CX0001]  
P87LPC767(ISP) [CX0001]  
P87LPC767@PLCC44(ISP) [CX0001]  
P87LPC767@SOIC20(ISP) [CX0001]  
P87LPC768(ISP) [CX0001]  
P87LPC768@SOIC20(ISP) [CX0001]  
P87LPC769(ISP) [CX0001]  
P87LPC769@PLCC44(ISP) [CX0001]  
P87LPC769@SOIC20(ISP) [CX0001]  
P87LPC778(ISP) [CX0001]  
P87LPC778@TSSOP20(ISP) [CX0001]  
P87LPC779(ISP) [CX0001]  
P87LPC779@TSSOP20(ISP) [CX0001]  
P89C138@PLCC44 [CX2044]  
P89C238 [CX0001]  
P89C238@TQFP44 [CX3005]  
P89C51B@PLCC44 [CX2044]  
P89C51RA+ [CX0001]  
P89C51RA+@TQFP44 [CX3005]  
P89C51RA2B@PLCC44 [CX2044]  
P89C51RB+ [CX0001]  
P89C51RB+@TQFP44 [CX3005]  
P89C51RB2B@PLCC44 [CX2044]  
P89C51RB2H [CX0001]  
P89C51RB2H@TQFP44 [CX3002]  
P89C51RC+@PLCC44 [CX2044]  
P89C51RC2B [CX0001]  
P89C51RC2B@TQFP44 [CX3005]  
P89C51RC2H@PLCC44 [CX2044]  
P89C51RD+ [CX0001]  
P89C51RD+@TQFP44 [CX3005]  
P89C51RD2B@PLCC44 [CX2044]  
P89C51RD2H [CX0001]  
P89C51RD2H@TQFP44 [CX3002]  
P89C51UB@PLCC44 [CX2044]  
P89C51UF [CX0001]  
P89C51UF@TQFP44 [CX3005]  
P89C51X2@PLCC44 [CX2044]  
P89C51X2B [CX0001]  
P89C51X2B@TQFP44 [CX3005]  
P89C51X2F@PLCC44 [CX2044]

P89C51X2F@TQFP44 [CX3005]  
P89C52@PLCC44 [CX2044]  
P89C52B [CX0001]  
P89C52B@TQFP44 [CX3005]  
P89C52UB@PLCC44 [CX2044]  
P89C52UF [CX0001]  
P89C52UF@TQFP44 [CX3005]  
P89C52X2@PLCC44 [CX2044]  
P89C52X2B [CX0001]  
P89C52X2B@TQFP44 [CX3005]  
P89C52X2F@PLCC44 [CX2044]  
P89C536@PLCC44 [CX2044]  
P89C54 [CX0001]  
P89C54@TQFP44 [CX3005]  
P89C54B@PLCC44 [CX2044]  
P89C54UB [CX0001]  
P89C54UB@TQFP44 [CX3005]  
P89C54UF@PLCC44 [CX2044]  
P89C54X2 [CX0001]  
P89C54X2@TQFP44 [CX3005]  
P89C54X2B@PLCC44 [CX2044]  
P89C54X2F [CX0001]  
P89C54X2F@TQFP44 [CX3005]  
P89C58@PLCC44 [CX2044]  
P89C58B [CX0001]  
P89C58B@TQFP44 [CX3005]  
P89C58UB@PLCC44 [CX2044]  
P89C58UF [CX0001]  
P89C58UF@TQFP44 [CX3005]  
P89C58X2@PLCC44 [CX2044]  
P89C58X2B [CX0001]  
P89C58X2B@TQFP44 [CX3005]  
P89C58X2F@PLCC44 [CX2044]  
P89C60X2 [CX0001]  
P89C60X2@TQFP44 [CX3005]  
P89C61X2@PLCC44 [CX2044]  
P89C660 [CX0001]  
P89C660@TQFP44 [CX3002]  
P89C662@PLCC44 [CX2044]  
P89C664 [CX0001]  
P89C664@TQFP44 [CX3002]  
P89C668@PLCC44 [CX2044]  
P89C669 [CX0001]  
P89C669@PLCC44 [CX2044]  
P89C669X2@LQFP44 [CX3005]  
P89C738 [CX0001]  
P89C738@TQFP44 [CX3005]  
P89C838@PLCC44 [CX2044]  
P89CV51RB2@PLCC44 [CX2044]  
P89CV51RC2@PLCC44 [CX2044]  
P89CV51RD2@PLCC44 [CX2044]  
P89LPC901(FD) [CX1045]  
P89LPC901(FN) [CX0001]  
P89LPC902(FD) [CX1045]  
P89LPC902(FN) [CX0001]  
P89LPC903(FD) [CX1045]  
P89LPC904(FD) [CX1045]  
P89LPC904(FN) [CX1045]  
P89LPC906(FD) [CX1045]

P89C52 [CX0001]  
P89C52@TQFP44 [CX3005]  
P89C52B@PLCC44 [CX2044]  
P89C52UB [CX0001]  
P89C52UB@TQFP44 [CX3005]  
P89C52UF@PLCC44 [CX2044]  
P89C52X2 [CX0001]  
P89C52X2@TQFP44 [CX3005]  
P89C52X2B@PLCC44 [CX2044]  
P89C52X2F [CX0001]  
P89C52X2F@TQFP44 [CX3005]  
P89C538@PLCC44 [CX2044]  
P89C54@PLCC44 [CX2044]  
P89C54B [CX0001]  
P89C54B@TQFP44 [CX3005]  
P89C54UB@PLCC44 [CX2044]  
P89C54UF [CX0001]  
P89C54UF@TQFP44 [CX3005]  
P89C54X2@PLCC44 [CX2044]  
P89C54X2B [CX0001]  
P89C54X2B@TQFP44 [CX3005]  
P89C54X2F@PLCC44 [CX2044]  
P89C58 [CX0001]  
P89C58@TQFP44 [CX3005]  
P89C58B@PLCC44 [CX2044]  
P89C58UB [CX0001]  
P89C58UB@TQFP44 [CX3005]  
P89C58UF@PLCC44 [CX2044]  
P89C58X2 [CX0001]  
P89C58X2@TQFP44 [CX3005]  
P89C58X2B@PLCC44 [CX2044]  
P89C58X2F [CX0001]  
P89C58X2F@TQFP44 [CX3005]  
P89C60X2@PLCC44 [CX2044]  
P89C61X2 [CX0001]  
P89C61X2@TQFP44 [CX3005]  
P89C660@PLCC44 [CX2044]  
P89C662 [CX0001]  
P89C662@TQFP44 [CX3002]  
P89C664@PLCC44 [CX2044]  
P89C668 [CX0001]  
P89C668@TQFP44 [CX3002]  
P89C669@LQFP44 [CX3005]  
P89C669X2 [CX0001]  
P89C669X2@PLCC44 [CX2044]  
P89C738@PLCC44 [CX2044]  
P89C838 [CX0001]  
P89C838@TQFP44 [CX3005]  
P89CV51RB2@TQFP44 [CX3005]  
P89CV51RC2@TQFP44 [CX3005]  
P89CV51RD2@TQFP44 [CX3005]  
P89LPC901(FD)(ISP) [CX0001]  
P89LPC901(FN)(ISP) [CX0001]  
P89LPC902(FD)(ISP) [CX0001]  
P89LPC902(FN)(ISP) [CX0001]  
P89LPC903(FD)(ISP) [CX0001]  
P89LPC904(FD)(ISP) [CX0001]  
P89LPC904(FN)(ISP) [CX0001]  
P89LPC906(FD)(ISP) [CX0001]

P89LPC907(FD) [CX1045] P89LPC907(FD)(ISP) [CX0001]  
P89LPC908(FD) [CX1045] P89LPC908(FD)(ISP) [CX0001]  
P89LPC9102(FTK)@HVSON10 [CX4007] P89LPC9103(FTK)@HVSON10 [CX4007]  
P89LPC9107(FDH)@TSSOP14 [CX1001] P89LPC9107(FN) [CX3001]  
P89LPC912(FDH)@TSSOP14 [CX1000]  
P89LPC912(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC913(FDH)@TSSOP14 [CX1000]  
P89LPC913(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC914(FDH)@TSSOP14 [CX1000]  
P89LPC914(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC915(FDH)@TSSOP14 [CX1000]  
P89LPC915(FDH)@TSSOP14(ISP) [CX0001]  
P89LPC916(FDH)@TSSOP16 [CX1000]  
P89LPC916(FDH)@TSSOP16(ISP) [CX0001]  
P89LPC917(FDH)@TSSOP16 [CX1000]  
P89LPC917(FDH)@TSSOP16(ISP) [CX0001]  
P89LPC920(FDH)@TSSOP20 [CX1000]  
P89LPC920(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC920(FN) [CX0001] P89LPC920(FN)(ISP) [CX0001]  
P89LPC9201(FDH)@TSSOP20 [CX1000]  
P89LPC9201(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9201(FN) [CX0001] P89LPC9201(FN)(ISP) [CX0001]  
P89LPC920A1(FDH)@TSSOP20 [CX1000]  
P89LPC920A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC920A1(FN) [CX0001] P89LPC920A1(FN)(ISP) [CX0001]  
P89LPC921(FDH)@TSSOP20 [CX1000]  
P89LPC921(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC921(FN) [CX0001] P89LPC921(FN)(ISP) [CX0001]  
P89LPC9211(FDH)@TSSOP20 [CX1000]  
P89LPC9211(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9211(FN) [CX0001] P89LPC9211(FN)(ISP) [CX0001]  
P89LPC921A1(FDH)@TSSOP20 [CX1000]  
P89LPC921A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC921A1(FN) [CX0001] P89LPC921A1(FN)(ISP) [CX0001]  
P89LPC922(FDH)@TSSOP20 [CX1000]  
P89LPC922(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC922(FN) [CX0001] P89LPC922(FN)(ISP) [CX0001]  
P89LPC9221(FDH)@TSSOP20 [CX1000]  
P89LPC9221(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9221(FN) [CX0001] P89LPC9221(FN)(ISP) [CX0001]  
P89LPC9221A1(FDH)@TSSOP20 [CX1000]  
P89LPC9221A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9221A1(FN) [CX0001] P89LPC9221A1(FN)(ISP) [CX0001]  
P89LPC922A1(FDH)@TSSOP20 [CX1000]  
P89LPC922A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC922A1(FN) [CX0001] P89LPC922A1(FN)(ISP) [CX0001]  
P89LPC924(FDH)@TSSOP20 [CX1000]  
P89LPC924(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC924(FN) [CX0001] P89LPC924(FN)(ISP) [CX0001]  
P89LPC9241(FDH)@TSSOP20 [CX1000]  
P89LPC9241(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9241(FN) [CX0001] P89LPC9241(FN)(ISP) [CX0001]  
P89LPC924A1(FDH)@TSSOP20 [CX1000]  
P89LPC924A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC924A1(FN) [CX0001] P89LPC924A1(FN)(ISP) [CX0001]  
P89LPC925(FDH)@TSSOP20 [CX1000]  
P89LPC925(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC925(FN) [CX0001] P89LPC925(FN)(ISP) [CX0001]  
P89LPC9251(FDH)@TSSOP20 [CX1000]

P89LPC9251(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC9251(FN) [CX0001] P89LPC9251(FN)(ISP) [CX0001]  
P89LPC925A1(FDH)@TSSOP20 [CX1000]  
P89LPC925A1(FDH)@TSSOP20(ISP) [CX0001]  
P89LPC925A1(FN) [CX0001] P89LPC925A1(FN)(ISP) [CX0001]  
P89LPC930(BA)@PLCC28 [CX2028]  
P89LPC930(BA)@PLCC28(ISP) [CX0001]  
P89LPC930(BDH)@TSSOP28 [CX1001]  
P89LPC930(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC9301(BA)@PLCC28 [CX2028] P89LPC9301(BDH)@TSSOP28 [CX1001]  
P89LPC9301FA [CX2028] P89LPC9301FDH [CX1001]  
P89LPC930FA [CX2028] P89LPC930FDH [CX1001]  
P89LPC931(BA)@PLCC28 [CX2028]  
P89LPC931(BA)@PLCC28(ISP) [CX0001]  
P89LPC931(BDH)@TSSOP28 [CX1001]  
P89LPC931(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC9311(BA)@PLCC28 [CX2028] P89LPC9311(BDH)@TSSOP28 [CX1001]  
P89LPC9311FA [CX2028] P89LPC9311FDH [CX1001]  
P89LPC931FA [CX2028] P89LPC931FDH [CX1001]  
P89LPC932(BA)@PLCC28 [CX2028] P89LPC932(BDH)@TSSOP28 [CX1001]  
P89LPC932(FA)@PLCC28 [CX2028] P89LPC93201BA@PLCC28 [CX2028]  
P89LPC93201BDH@TSSOP28 [CX1001] P89LPC93201FA@PLCC28 [CX2028]  
P89LPC93201FDH@TSSOP28 [CX1001] P89LPC93201FHN@QFN28 [CX4014]  
P89LPC9321BA@PLCC28 [CX2028] P89LPC9321BDH@TSSOP28 [CX1001]  
P89LPC9321FA@PLCC28 [CX2028] P89LPC9321FDH@TSSOP28 [CX1001]  
P89LPC9321FHN@QFN28 [CX4014] P89LPC932A1(BA)@PLCC28 [CX2028]  
P89LPC932A1(BA)@PLCC28(ISP) [CX0001]  
P89LPC932A1(BDH)@TSSOP28 [CX1001]  
P89LPC932A1(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC932A1(FA)@PLCC28 [CX2028]  
P89LPC932A1(FDH)@TSSOP28 [CX1001]  
P89LPC932A1(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC932A1(FHN)@HVQFN28 [CX4014]  
P89LPC932A1(FHN)@HVQFN28(ISP) [CX0001]  
P89LPC933(BDH)@TSSOP28 [CX1001]  
P89LPC933(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC933(FDH)@TSSOP28 [CX1001]  
P89LPC933(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC933(HDH)@TSSOP28 [CX1001] P89LPC9331(BDH)@TSSOP28 [CX1001]  
P89LPC9331(FDH)@TSSOP28 [CX1001] P89LPC9331(HDH)@TSSOP28 [CX1001]  
P89LPC934(BDH)@TSSOP28 [CX1001]  
P89LPC934(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC934(FDH)@TSSOP28 [CX1001]  
P89LPC934(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC93401(FDH)@TSSOP28 [CX1001]  
P89LPC93401V [CX0001] P89LPC9341(BDH)@TSSOP28 [CX1001]  
P89LPC9341(FDH)@TSSOP28 [CX1001] P89LPC9341V [CX0001]  
P89LPC935(BA)@PLCC28 [CX2028]  
P89LPC935(BA)@PLCC28(ISP) [CX0001]  
P89LPC935(BDH)@TSSOP28 [CX1001]  
P89LPC935(BDH)@TSSOP28(ISP) [CX0001]  
P89LPC935(FA)@PLCC28 [CX2028]  
P89LPC935(FA)@PLCC28(ISP) [CX0001]  
P89LPC935(FDH)@TSSOP28 [CX1001]  
P89LPC935(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC935(FHN)@HVQFN28 [CX4014]  
P89LPC935(FHN)@HVQFN28(ISP) [CX0001]  
P89LPC93501BA@PLCC28 [CX2028] P89LPC93501BDH@TSSOP28 [CX1001]  
P89LPC93501FA@PLCC28 [CX2028] P89LPC93501FDH@TSSOP28 [CX1001]

P89LPC93501FHN@QFN28 [CX4014] P89LPC9351BA@PLCC28 [CX2028]  
P89LPC9351BDH@TSSOP28 [CX1001] P89LPC9351FA@PLCC28 [CX2028]  
P89LPC9351FDH@TSSOP28 [CX1001] P89LPC9351FHN@QFN28 [CX4014]  
P89LPC936(FA)@PLCC28 [CX2028] P89LPC936(FDH)@TSSOP28 [CX1001]  
P89LPC9361(FA)@PLCC28 [CX2028] P89LPC9361(FDH)@TSSOP28 [CX1001]  
P89LPC938(FA)@PLCC28 [CX2028]  
P89LPC938(FA)@PLCC28(ISP) [CX0001]  
P89LPC938(FDH)@TSSOP28 [CX1001]  
P89LPC938(FDH)@TSSOP28(ISP) [CX0001]  
P89LPC938(FHN)@HVQFN28 [CX4014]  
P89LPC938(FHN)@HVQFN28(ISP) [CX0001]  
P89LPC93801BA@PLCC28 [CX2028] P89LPC93801BDH@TSSOP28 [CX1001]  
P89LPC93801FA@PLCC28 [CX2028] P89LPC93801FDH@TSSOP28 [CX1001]  
P89LPC93801FHN@QFN28 [CX4014] P89LPC9381BA@PLCC28 [CX2028]  
P89LPC9381BDH@TSSOP28 [CX1001] P89LPC9381FA@PLCC28 [CX2028]  
P89LPC9381FDH@TSSOP28 [CX1001] P89LPC9381FHN@QFN28 [CX4014]  
P89LPC9401(FBD)@LQFP64(ISP) [CX0001]  
P89LPC9408(FBD)@LQFP64(ISP) [CX0001]  
P89LPC952@LQFP44 [CX3005] P89LPC952@LQFP44(ISP) [CX0001]  
P89LPC952@LQFP48 [CX3007] P89LPC952@LQFP48(ISP) [CX0001]  
P89LPC952@PLCC44 [CX2044] P89LPC952@PLCC44(ISP) [CX0001]  
P89LPC954@LQFP44 [CX3005] P89LPC954@LQFP44(ISP) [CX0001]  
P89LPC954@LQFP48 [CX3007] P89LPC954@LQFP48(ISP) [CX0001]  
P89LPC954@PLCC44 [CX2044] P89LPC954@PLCC44(ISP) [CX0001]  
P89LPC970FDH@TSSOP20 [CX1000]  
P89LPC970FDH@TSSOP20(serial) [CX1000]  
P89LPC970FN [CX0001] P89LPC970FN(serial) [CX0001]  
P89LPC971FDH@TSSOP20 [CX1000]  
P89LPC971FDH@TSSOP20(serial) [CX1000]  
P89LPC971FN [CX0001] P89LPC971FN(serial) [CX0001]  
P89LPC972FDH@TSSOP20 [CX1000]  
P89LPC972FDH@TSSOP20(serial) [CX1000]  
P89LPC972FN [CX0001] P89LPC972FN(serial) [CX0001]  
P89LPC980FDH@TSSOP28 [CX1001]  
P89LPC980FDH@TSSOP28(serial) [CX1001]  
P89LPC982FDH@TSSOP28 [CX1001]  
P89LPC982FDH@TSSOP28(serial) [CX1001]  
P89LPC983FA@PLCC28 [CX2028]  
P89LPC983FA@PLCC28(serial) [CX2028]  
P89LPC983FDH@TSSOP28 [CX1001]  
P89LPC983FDH@TSSOP28(serial) [CX1001]  
P89LPC985FA@PLCC28 [CX2028]  
P89LPC985FA@PLCC28(serial) [CX2028]  
P89LPC985FDH@TSSOP28 [CX1001]  
P89LPC985FDH@TSSOP28(serial) [CX1001]  
P89LPC9902FTK [CX4047] P89LPC9903FTK [CX4047]  
P89LV51RB2 [CX0001] P89LV51RB2@PLCC44 [CX2044]  
P89LV51RB2@TQFP44 [CX3005] P89LV51RB2FA@PLCC44 [CX2044]  
P89LV51RB2FBC@TQFP44 [CX3005] P89LV51RB2FN [CX0001]  
P89LV51RC2 [CX0001] P89LV51RC2@PLCC44 [CX2044]  
P89LV51RC2@TQFP44 [CX3005] P89LV51RC2FA@PLCC44 [CX2044]  
P89LV51RC2FBC@TQFP44 [CX3005] P89LV51RC2FN [CX0001]  
P89LV51RD2 [CX0001] P89LV51RD2(new) [CX0001]  
P89LV51RD2(new)@PLCC44 [CX2044] P89LV51RD2(new)@TQFP44 [CX3005]  
P89LV51RD2@PLCC44 [CX2044] P89LV51RD2@TQFP44 [CX3005]  
P89LV51RD2BA(new)@PLCC44 [CX2044]  
P89LV51RD2BA@PLCC44 [CX2044]  
P89LV51RD2BBC(new)@TQFP44 [CX3005]  
P89LV51RD2BBC@TQFP44 [CX3005] P89LV51RD2BN [CX0001]

P89LV51RD2BN(new) [CX0001]  
P89LV51RD2FA(new)@PLCC44 [CX2044]  
P89LV51RD2FA@PLCC44 [CX2044]  
P89LV51RD2FBC(new)@TQFP44 [CX3005]  
P89LV51RD2FBC@TQFP44 [CX3005]  
P89LV51RD2FN(new) [CX0001]  
P89V51RB2@PLCC44 [CX2044]  
P89V51RB2FA@PLCC44 [CX2044]  
P89V51RB2FN [CX0001]  
P89V51RC2@PLCC44 [CX2044]  
P89V51RC2FA@PLCC44 [CX2044]  
P89V51RC2FN [CX0001]  
P89V51RD2(new) [CX0001]  
P89V51RD2(new)@TQFP44 [CX3005]  
P89V51RD2@TQFP44 [CX3005]  
P89V51RD2BA@PLCC44 [CX2044]  
P89V51RD2BBC(new)@TQFP44 [CX3005]  
P89V51RD2BBC@TQFP44 [CX3005]  
P89V51RD2BN(new) [CX0001]  
P89V51RD2FA@PLCC44 [CX2044]  
P89V51RD2FBC(new)@TQFP44 [CX3005]  
P89V51RD2FBC@TQFP44 [CX3005]  
P89V51RD2FN(new) [CX0001]  
P89V52X2(ISP) [CX0001]  
P89V52X2@PLCC44(ISP) [CX0001]  
P89V52X2@TQFP44(ISP) [CX0001]  
P89V54X2(ISP) [CX0001]  
P89V54X2@PLCC44(ISP) [CX0001]  
P89V54X2@TQFP44(ISP) [CX0001]  
P89V660@TQFP44 [CX3005]  
P89V662@TQFP44 [CX3005]  
P89V664@TQFP44 [CX3005]  
PSD301L@PLCC44 [CX2044]  
PSD302L@PLCC44 [CX2044]  
PSD303L@PLCC44 [CX2044]  
PSD311L@PLCC44 [CX2044]  
PSD312L@PLCC44 [CX2044]  
PSD313@TQFP44 [CX3003]  
PSD313-B@TQFP44 [CX3003]  
PSD313L@TQFP44 [CX3003]  
PXAC37@TQFP44 [CX3003]  
PXAG17@TQFP44 [CX3003]  
PXAG27@TQFP44 [CX3003]  
PXAG37@TQFP44 [CX3003]  
PXAG39@TQFP44 [CX3003]  
PXAG39K@TQFP44 [CX3003]  
PXAG49@TQFP44 [CX3003]  
PXAG49K@TQFP44 [CX3003]  
TDA11106PS@SDIP64 [CX0064]  
TDA11115PS@SDIP64 [CX0064]  
TDA11125PS@SDIP64 [CX0064]  
TDA11135PS@SDIP64 [CX0064]  
TDA11142PS@SDIP64 [CX0064]  
TDA11146PS@SDIP64 [CX0064]  
TDA11156PS@SDIP64 [CX0064]  
TDA12136PS@SDIP64 [CX0064]  
TDA12156PS@SDIP64 [CX0064]  
TDA12166PS@SDIP64 [CX0064]  
TDA12176PS@SDIP64 [CX0064]  
P89LV51RD2FN [CX0001]  
P89V51RB2 [CX0001]  
P89V51RB2@TQFP44 [CX3005]  
P89V51RB2FBC@TQFP44 [CX3005]  
P89V51RC2 [CX0001]  
P89V51RC2@TQFP44 [CX3005]  
P89V51RC2FBC@TQFP44 [CX3005]  
P89V51RD2 [CX0001]  
P89V51RD2(new)@PLCC44 [CX2044]  
P89V51RD2@PLCC44 [CX2044]  
P89V51RD2BA(new)@PLCC44 [CX2044]  
P89V51RD2BN [CX0001]  
P89V51RD2FA(new)@PLCC44 [CX2044]  
P89V51RD2FN [CX0001]  
P89V52X2 [CX0001]  
P89V52X2@PLCC44 [CX2044]  
P89V52X2@TQFP44 [CX3005]  
P89V54X2 [CX0001]  
P89V54X2@PLCC44 [CX2044]  
P89V54X2@TQFP44 [CX3005]  
P89V660@PLCC44 [CX2044]  
P89V662@PLCC44 [CX2044]  
P89V664@PLCC44 [CX2044]  
PSD301@PLCC44 [CX2044]  
PSD302@PLCC44 [CX2044]  
PSD303@PLCC44 [CX2044]  
PSD311@PLCC44 [CX2044]  
PSD312@PLCC44 [CX2044]  
PSD313@PLCC44 [CX2044]  
PSD313-B@PLCC44 [CX2044]  
PSD313L@PLCC44 [CX2044]  
PXAC37@PLCC44 [CX2044]  
PXAG17@PLCC44 [CX2044]  
PXAG27@PLCC44 [CX2044]  
PXAG37@PLCC44 [CX2044]  
PXAG39@PLCC44 [CX2044]  
PXAG39K@PLCC44 [CX2044]  
PXAG49@PLCC44 [CX2044]  
PXAG49K@PLCC44 [CX2044]  
TDA11105PS@SDIP64 [CX0064]  
TDA11112PS@SDIP64 [CX0064]  
TDA11116PS@SDIP64 [CX0064]  
TDA11126PS@SDIP64 [CX0064]  
TDA11136PS@SDIP64 [CX0064]  
TDA11145PS@SDIP64 [CX0064]  
TDA11155PS@SDIP64 [CX0064]  
TDA12135PS@SDIP64 [CX0064]  
TDA12155PS@SDIP64 [CX0064]  
TDA12165PS@SDIP64 [CX0064]  
TDA12175PS@SDIP64 [CX0064]  
TDA12185PS@SDIP64 [CX0064]



TDA12186PS@SDIP64 [CX0064]  
TDA12196PS@SDIP64 [CX0064]

TDA12195PS@SDIP64 [CX0064]

## PJ

### E (E) PROM/FRAM/NVRAM

PJ24C02 [CX0001]  
PJ24C02@TSSOP8 [CX1059]

PJ24C02@SOIC8 [CX1045]

## PMC

### E (E) PROM/FRAM/NVRAM

PM24C64 [CX0001]  
PM24C64@TSOP8 [CX1059]  
PM25LD512(Q)@WSON8 [CX4005]  
PM25LQ032@SOIC8 [CX1044#1]  
PM25LQ040(B)@SOIC8 [CX1044#1]  
PM25LQ040(S)@SOIC8 [CX1045#1]  
PM25LV010(Q)@WSON8 [CX4005]  
PM25LV010A(B)@SOIC8 [CX1044]  
PM25LV010A(S)@SOIC8 [CX1045]  
PM25LV020(Q)@WSON8 [CX4005#1]  
PM25LV040(B)@SOIC8 [CX1044#1]  
PM25LV040(S)@SOIC8 [CX1045#1]  
PM25LV512(Q)@WSON8 [CX4005]  
PM25LV512A(B)@SOIC8 [CX1044]  
PM25LV512A(S)@SOIC8 [CX1045]  
PM29F002B [CX0001]  
PM29F002T [CX0001]  
PM29F004B [CX0001]  
PM29F004T [CX0001]  
PM29LV002B [CX0001]  
PM29LV002B@VSOP32 [CX1003]  
PM29LV002T@PLCC32 [CX2032]  
PM29LV004B@PLCC32 [CX2032]  
PM29LV004T@PLCC32 [CX2032]  
PM29LV104RB@PLCC32 [CX2032]  
PM29LV104RT@PLCC32 [CX2032]  
PM37LV512 [CX0001]  
PM37LV512@VSOP32 [CX1003]  
PM39F010@PLCC32 [CX2032]  
PM39F020 [CX0001]  
PM39F020@VSOP32 [CX1003]  
PM39F040@PLCC32 [CX2032]  
PM39LV010@PLCC32 [CX2032]  
PM39LV010R@PLCC32 [CX2032]  
PM39LV020@PLCC32 [CX2032]  
PM39LV040@PLCC32 [CX2032]  
PM39LV512@PLCC32 [CX2032]  
PM39LV512R@PLCC32 [CX2032]  
PM49FL002T@PLCC32 [CX2032]  
PM49FL004T@PLCC32 [CX2032]  
PM49FL008T@PLCC32 [CX2032]  
PM49LP002T@PLCC32 [CX2032]

PM24C64@SOIC8 [CX1045]  
PM25LD512(B)@SOIC8 [CX1044]  
PM25LD512(S)@SOIC8 [CX1045]  
PM25LQ032@WSON8 [CX4006#1]  
PM25LQ040(Q)@WSON8 [CX4005#1]  
PM25LV010(B)@SOIC8 [CX1044]  
PM25LV010(S)@SOIC8 [CX1045]  
PM25LV010A(Q)@WSON8 [CX4005]  
PM25LV020(B)@SOIC8 [CX1044#1]  
PM25LV020(S)@SOIC8 [CX1045#1]  
PM25LV040(Q)@WSON8 [CX4005#1]  
PM25LV512(B)@SOIC8 [CX1044]  
PM25LV512(S)@SOIC8 [CX1045]  
PM25LV512A(Q)@WSON8 [CX4005]  
PM25LV512A@TSSOP8 [CX1059]  
PM29F002B@PLCC32 [CX2032]  
PM29F002T@PLCC32 [CX2032]  
PM29F004B@PLCC32 [CX2032]  
PM29F004T@PLCC32 [CX2032]  
PM29LV002B@PLCC32 [CX2032]  
PM29LV002T [CX0001]  
PM29LV002T@VSOP32 [CX1003]  
PM29LV004B@VSOP32 [CX1003]  
PM29LV004T@VSOP32 [CX1003]  
PM29LV104RB@VSOP32 [CX1003]  
PM29LV104RT@VSOP32 [CX1003]  
PM37LV512@PLCC32 [CX2032]  
PM39F010 [CX0001]  
PM39F010@VSOP32 [CX1003]  
PM39F020@PLCC32 [CX2032]  
PM39F040 [CX0001]  
PM39F040@VSOP32 [CX1003]  
PM39LV010@VSOP32 [CX1003]  
PM39LV010R@VSOP32 [CX1003]  
PM39LV020@VSOP32 [CX1003]  
PM39LV040@VSOP32 [CX1003]  
PM39LV512@VSOP32 [CX1003]  
PM39LV512R@VSOP32 [CX1003]  
PM49FL002T@VSOP32 [CX1003]  
PM49FL004T@VSOP32 [CX1003]  
PM49FL008T@VSOP32 [CX1003]  
PM49LP002T@VSOP32 [CX1003]

## PORTEK

### E (E) PROM/FRAM/NVRAM

PTK24A02T [CX0001]	PTK24A02T@SOIC8 [CX1045]
PTK24A04T [CX0001]	PTK24A04T@SOIC8 [CX1045]
PTK24A08T [CX0001]	PTK24A08T@SOIC8 [CX1045]
PTK24A16T [CX0001]	PTK24A16T@SOIC8 [CX1045]

## POWERFLASH

### E (E) PROM/FRAM/NVRAM

ASU1GA30HT@TSOP48 [CX1004-3]

## POWER-RAIL

### MICROCONTROLLER

MP01002 [CX0001]	MP01004 [CX0001]
MP01006 [CX0001]	MP01006XQN32 [CX4039-5]
MP01006XQP48 [CX3007-5]	MP01006XQP64 [CX3011-5]
MP01008 [CX0001]	MP01008XLQ48 [CX3007]
MP01008XLQ64 [CX3011]	MP01008XLQ80 [CX3060]
MP01010 [CX0001]	MP3004@LQFP48 [CX0001]
MP3004@LQFP64 [CX0001]	MP3004@QFP32 [CX0001]
MP3004@QFP64 [CX0001]	MP3004@SSOP28 [CX0001]
MP4132XLQ64 [CX3011]	MP6016X [CX0001]
MP6116X [CX0001]	MP6116XQN32 [CX4039-5]
MP6116XQP48 [CX3007-5]	MP6116XQP64 [CX3011-5]
MP8132XLQ48 [CX3007]	MP8132XLQ64 [CX3011]
MP8132XLQ80 [CX3060]	

## PSS

### E (E) PROM/FRAM/NVRAM

PS24C256 [CX0001]	PS24C256@SOIC8 [CX1045]
-------------------	-------------------------

## PTC

### E (E) PROM/FRAM/NVRAM

PT28C020 [CX0001]	PT28C020@PLCC32 [CX2032]
PT28C040 [CX0001]	PT28C040@PLCC32 [CX2032]
PT29C020 [CX0001]	PT29C020@PLCC32 [CX2032]
PT29C040 [CX0001]	PT29C040@PLCC32 [CX2032]

### MICROCONTROLLER

PT8936 [CX0001]	PT8936@PLCC44 [CX2044]
PT8936@TQFP44 [CX3002]	PT8956 [CX0001]
PT8956@PLCC44 [CX2044]	PT8956@TQFP44 [CX3002]

## QISDA-CUSTOMER

### E ( E ) PROM / FRAM / NVRAM

AT24C32C [CX0001]  
RM24C32C [CX0001]

BR24S32 [CX0001]

## QIXIN

### MICROCONTROLLER

LS2051 [CX0001]  
LS4051 [CX0001]

LS2051@SOIC20 [CX1031]  
LS4051@SOIC20 [CX1031]

## Quick Pulse

### E ( E ) PROM / FRAM / NVRAM

27010 [CX0001]  
27040 [CX0001]  
27210 [CX0001]  
27512 [CX0001]

27011 [CX0001]  
27128A [CX0001]  
27256 [CX0001]  
2764A [CX0001]

## RAMTRON

### E ( E ) PROM / FRAM / NVRAM

FM1208 [CX0001]  
FM1608 [CX0001]  
FM1608B [CX0001]  
FM16W08 [CX0001]  
FM1808 [CX0001]  
FM1808B [CX0001]  
FM18L08 [CX0001]  
FM18W08 [CX0001]  
FM20L08@TSOP32 [CX1053]  
FM21LD16@FBGA48 [CX5085]  
FM22LD16@FBGA48 [CX5085]  
FM24164 [CX0001]  
FM24C04(P) [CX0001]  
FM24C04A(P) [CX0001]  
FM24C04B@SOIC8 [CX1045]  
FM24C08A [CX0001]  
FM24C16(P) [CX0001]  
FM24C16A(P) [CX0001]  
FM24C16B@SOIC8 [CX1045]  
FM24C256@SOIC8 [CX1045]  
FM24C64 [CX0001]  
FM24C64B@SOIC8 [CX1045]  
FM24CL04 [CX0001]  
FM24CL04B@SOIC8 [CX1045]  
FM24CL16@SOIC8 [CX1045]  
FM24CL16B@TDFN8 [CX0001]  
FM24CL64B@SOIC8 [CX1045]

FM1208@SOIC24 [CX1033]  
FM1608@SOIC28 [CX1033]  
FM1608B@SOIC28 [CX1033]  
FM16W08@SOIC28 [CX1033]  
FM1808@SOIC28 [CX1033]  
FM1808B@SOIC28 [CX1033]  
FM18L08@SOIC28 [CX1033]  
FM18W08@SOIC28 [CX1033]  
FM21L16@TSOP44 [CX1046]  
FM22L16@TSOP44 [CX1046]  
FM23MLD16@FBGA48 [CX5002]  
FM24164@SOIC8 [CX1045]  
FM24C04(S)@SOP8 [CX1045]  
FM24C04A(S)@SOP8 [CX1045]  
FM24C04C@SOIC8 [CX1045]  
FM24C08A@SOP8 [CX1045]  
FM24C16(S)@SOP8 [CX1045]  
FM24C16A(S)@SOP8 [CX1045]  
FM24C16C@SOIC8 [CX1045]  
FM24C512@SOIC8 [CX1044]  
FM24C64@SOIC8 [CX1045]  
FM24C64C@SOIC8 [CX1045]  
FM24CL04@SOIC8 [CX1045]  
FM24CL16 [CX0001]  
FM24CL16B@SOIC8 [CX1045]  
FM24CL64@SOIC8 [CX1045]  
FM24CL64B-GA@SOIC8 [CX1045]

FM24V01@SOIC8 [CX1045]  
FM24V05@SOIC8 [CX1044]  
FM24VN01@SOIC8 [CX1045]  
FM24W256@SOIC8(150mil) [CX1045]  
FM25040 [CX0001]  
FM25040B@SOIC8 [CX1045]  
FM25160@SOIC8 [CX1045]  
FM25640@SOIC8 [CX1016]  
FM25640B@SOIC8 [CX1016]  
FM25C160@SOIC8 [CX1045]  
FM25CL64 [CX0001]  
FM25CL64B@SOIC8 [CX1045]  
FM25E64@SOIC8 [CX1045]  
FM25H20@TDFN8 [CX0001]  
FM25L16 [CX0001]  
FM25L256 [CX0001]  
FM25L256@TDFN8 [CX0001]  
FM25L256B@SOIC8 [CX1045#1]  
FM25L512 [CX0001]  
FM25LX64@SOIC8 [CX1045]  
FM25V01@SOIC8 [CX1045#1]  
FM25V02@TDFN8 [CX0001]  
FM25V10@SOIC8 [CX1045#1]  
FM25V20@TDFN8 [CX4005#1]  
FM28V020@SI0C28 [CX1033]  
FM28V100@TSOP32 [CX1053]  
FM30C256@SOIC20 [CX1033]  
FM3116@SOIC14 [CX1030]  
FM3164@SOIC14 [CX1016]  
FM3808 [CX0001]  
FM24V02@SOIC8 [CX1045]  
FM24V10@SOIC8 [CX1045]  
FM24VN02@SOIC8 [CX1045]  
FM24W256@SOIC8(200mil) [CX1045]  
FM25040@SOIC8 [CX1045]  
FM25160 [CX0001]  
FM25640 [CX0001]  
FM25640B [CX0001]  
FM25C160 [CX0001]  
FM25CL04@SOIC8 [CX1045]  
FM25CL64@SOIC8 [CX1045]  
FM25CL64B@TDFN8 [CX4005]  
FM25H20@SOIC8 [CX1045#1]  
FM25L04B@SOIC8 [CX1045]  
FM25L16@SOIC8 [CX1045]  
FM25L256@SOIC8 [CX1045#1]  
FM25L256B [CX0001]  
FM25L256B@TDFN8 [CX0001]  
FM25L512@SOIC8 [CX1045#1]  
FM25P16@SOIC8 [CX1045]  
FM25V02@SOIC8 [CX1045#1]  
FM25V05@SOIC8 [CX1045#1]  
FM25V20@SOIC8 [CX1045#1]  
FM25W256@SOIC8 [CX1045#1]  
FM28V020@TSOP32 [CX1053]  
FM28V200@TSOP32 [CX1053]  
FM3104@SOIC14 [CX1030]  
FM31256@SOIC14 [CX1016]  
FM31L278@SOIC14 [CX1016]  
FM3808@TSOP32 [CX1003]

## MICROCONTROLLER

VMX51C900 [CX0001]  
VMX51C900@TQFP44 [CX3003]  
VRS1000@PLCC44 [CX2044]  
VRS1100 [CX0001]  
VRS1100@TQFP44 [CX3003]  
VRS51C1000@PLCC44 [CX2044]  
VRS51C1100 [CX0001]  
VRS51C1100@TQFP44 [CX3003]  
VRS51C540@PLCC44 [CX2044]  
VRS51C550 [CX0001]  
VRS51C550@TQFP44 [CX3003]  
VRS51C560@PLCC44 [CX2044]  
VRS51C570 [CX0001]  
VRS51C570@TQFP44 [CX3003]  
VRS51C580@PLCC44 [CX2044]  
VRS51C700 [CX0001]  
VRS51C700@TQFP44 [CX3003]  
VRS51L1050@PLCC44 [CX2044]  
VRS51L540 [CX0001]  
VRS51L540@TQFP44 [CX3003]  
VRS51L550@PLCC44 [CX2044]  
VRS51L560 [CX0001]  
VRS51L560@TQFP44 [CX3003]  
VRS51L570@PLCC44 [CX2044]  
VRS51L580 [CX0001]  
VRS51L580@TQFP44 [CX3003]  
VMX51C900@PLCC44 [CX2044]  
VRS1000 [CX0001]  
VRS1000@TQFP44 [CX3003]  
VRS1100@PLCC44 [CX2044]  
VRS51C1000 [CX0001]  
VRS51C1000@TQFP44 [CX3003]  
VRS51C1100@PLCC44 [CX2044]  
VRS51C540 [CX0001]  
VRS51C540@TQFP44 [CX3003]  
VRS51C550@PLCC44 [CX2044]  
VRS51C560 [CX0001]  
VRS51C560@TQFP44 [CX3003]  
VRS51C570@PLCC44 [CX2044]  
VRS51C580 [CX0001]  
VRS51C580@TQFP44 [CX3003]  
VRS51C700@PLCC44 [CX2044]  
VRS51L1050 [CX0001]  
VRS51L1050@TQFP44 [CX3003]  
VRS51L540@PLCC44 [CX2044]  
VRS51L550 [CX0001]  
VRS51L550@TQFP44 [CX3003]  
VRS51L560@PLCC44 [CX2044]  
VRS51L570 [CX0001]  
VRS51L570@TQFP44 [CX3003]  
VRS51L580@PLCC44 [CX2044]  
VRS51X540 [CX0001]

VRS51X540@PLCC44 [CX2044]  
VRS51X550 [CX0001]  
VRS51X550@TQFP44 [CX3003]  
VRS51X560@PLCC44 [CX2044]  
VRS51X570 [CX0001]  
VRS51X570@TQFP44 [CX3003]  
VRS51X580@PLCC44 [CX2044]  
VRS540 [CX0001]  
VRS540@TQFP44 [CX3003]  
VRS550@PLCC44 [CX2044]  
VRS560 [CX0001]  
VRS560@TQFP44 [CX3003]  
VRS570@PLCC44 [CX2044]  
VRS580 [CX0001]  
VRS580@TQFP44 [CX3003]  
VRS700@PLCC44 [CX2044]  
VRS900 [CX0001]  
VRS900@TQFP44 [CX3003]

VRS51X540@TQFP44 [CX3003]  
VRS51X550@PLCC44 [CX2044]  
VRS51X560 [CX0001]  
VRS51X560@TQFP44 [CX3003]  
VRS51X570@PLCC44 [CX2044]  
VRS51X580 [CX0001]  
VRS51X580@TQFP44 [CX3003]  
VRS540@PLCC44 [CX2044]  
VRS550 [CX0001]  
VRS550@TQFP44 [CX3003]  
VRS560@PLCC44 [CX2044]  
VRS570 [CX0001]  
VRS570@TQFP44 [CX3003]  
VRS580@PLCC44 [CX2044]  
VRS700 [CX0001]  
VRS700@TQFP44 [CX3003]  
VRS900@PLCC44 [CX2044]

## RATO

### E (E) PROM/FRAM/NVRAM

RT24A02 [CX0001]  
RT24A02@TSSOP8 [CX1059]  
RT24A04@SOIC8 [CX1045]  
RT24A08 [CX0001]  
RT24A08@TSSOP8 [CX1059]  
RT24A16@SOIC8 [CX1045]  
RT93C46B(16bit) [CX0001]  
RT93C46B(16bit)@TSSOP8 [CX1059]  
RT93LC46(08bit)@SOIC8 [CX1045]  
RT93LC46(16bit) [CX0001]  
RT93LC46(16bit)@TSSOP8 [CX1059]

RT24A02@SOIC8 [CX1045]  
RT24A04 [CX0001]  
RT24A04@TSSOP8 [CX1059]  
RT24A08@SOIC8 [CX1045]  
RT24A16 [CX0001]  
RT24A16@TSSOP8 [CX1059]  
RT93C46B(16bit)@SOIC8 [CX1045]  
RT93LC46(08bit) [CX0001]  
RT93LC46(08bit)@TSSOP8 [CX1059]  
RT93LC46(16bit)@SOIC8 [CX1045]

## RAYDIUM

### E (E) PROM/FRAM/NVRAM

RM24C02@SOP8 [CX1045]  
RM24C08@SOP8 [CX1045]  
RM24C16@SOP8 [CX1045]  
RM24C64@SOP8 [CX1045]

RM24C04@SOP8 [CX1045]  
RM24C128@SOP8 [CX1045]  
RM24C32@SOP8 [CX1045]

## REALTEK

### MICROCONTROLLER

RTD2120L@LQFP48 [CX3007]

RTD2120L@PLCC44 [CX2044]

## RENESAS

### E (E) PROM/FRAM/NVRAM

HN58C256A(FP)@SOP28 [CX1033]

HN58C256A(P) [CX0001]

HN58C256A(T)@TSOP28 [CX1024]  
HN58V24256 [CX0001]  
HN58V24256@TSSOP14 [CX1000]  
HN58V24512@SOIC8 [CX1045]  
HN58W241000@SOIC8 [CX1045]  
HN58X2402@SOIC8 [CX1045]  
HN58X2404 [CX0001]  
HN58X2404@TSSOP8 [CX1059]  
HN58X2408@SOIC8 [CX1045]  
HN58X24128 [CX0001]  
HN58X2416 [CX0001]  
HN58X2416@TSSOP8 [CX1059]  
HN58X24256@SOIC8 [CX1045]  
HN58X2432@SOIC8 [CX1045]  
HN58X24512 [CX0001]  
HN58X2464 [CX0001]  
HN58X2464@TSSOP8 [CX1059]  
HN58X2502@TSSOP8 [CX1059]  
HN58X2504@TSSOP8 [CX1059]  
HN58X2508@TSSOP8 [CX1059]  
HN58X25128@TSSOP14 [CX1000]  
HN58X2516@TSSOP8 [CX1059]  
HN58X25256@TSSOP14 [CX1000]  
HN58X2532@TSSOP8 [CX1059]  
HN58X2564@TSSOP8 [CX1059]  
M5L2732A [CX0001]  
M5M29KB641(AVP)@TSOP48 [CX1004]  
M5M29KE131BV@TSOP48 [CX1004]  
M5M29KT641(AVP)@TSOP48 [CX1004]  
M6MG3T641S16TP@TSOP52 [CX1009]  
M6MGB321S4TP@TSOP52 [CX1009]  
M6MGB32BS4WG@CSP66 [CX5001]  
M6MGB331S8KT@TSOP52 [CX1009]  
M6MGB641S16TP@TSOP52 [CX1009]  
M6MGB641S8TP@TSOP52 [CX1009]  
M6MGB64BM17AWG@CSP67 [CX5053]  
M6MGB64BM34CWG@CSP67 [CX5053]  
M6MGB64BS8WG@CSP67 [CX5001]  
M6MGD13TW34DWG@CSP72 [CX5053]  
M6MGT166S4B(WG)@FBGA72 [CX5001]  
M6MGT321S8TP@TSOP52 [CX1009]  
M6MGT32BS8WG@CSP66 [CX5001]  
M6MGT33BS8AWG@CSP66 [CX5001]  
M6MGT641S4TP@TSOP52 [CX1009]  
M6MGT647M34CKT@TSOP52 [CX1009]  
M6MGT64BM34CDG@CSP88 [CX5053]  
M6MGT64BS4WG@CSP67 [CX5001]  
MC10233@BGA208 [CX5226#1]  
R1EX24002A@SOP8 [CX1045]  
R1EX24004A@SOP8 [CX1045]  
R1EX24008A@SOP8 [CX1045]  
R1EX24016A@SOP8 [CX1045]  
R1EX24032A@SOP8 [CX1045]  
R1EX24064A@SOP8 [CX1045]  
R1EX24128A@SOP8 [CX1045]  
R1EX24256A@SOP8 [CX1045]  
R1EX24512A@SOP8 [CX1045]  
R1EX25002A@SOIC8 [CX1045]  
R1EX25004A@SOIC8 [CX1045]

HN58C257A(T)@TSOP32 [CX1032]  
HN58V24256@SOIC8 [CX1045]  
HN58V24512 [CX0001]  
HN58W241000 [CX0001]  
HN58X2402 [CX0001]  
HN58X2402@TSSOP8 [CX1059]  
HN58X2404@SOIC8 [CX1045]  
HN58X2408 [CX0001]  
HN58X2408@TSSOP8 [CX1059]  
HN58X24128@SOIC8 [CX1045]  
HN58X2416@SOIC8 [CX1045]  
HN58X24256 [CX0001]  
HN58X2432 [CX0001]  
HN58X2432@TSSOP8 [CX1059]  
HN58X24512@SOIC8 [CX1045]  
HN58X2464@SOIC8 [CX1045]  
HN58X2502@SOIC8 [CX1045]  
HN58X2504@SOIC8 [CX1045]  
HN58X2508@SOIC8 [CX1045]  
HN58X25128@SOIC8 [CX1045]  
HN58X2516@SOIC8 [CX1045]  
HN58X25256@SOIC8 [CX1045]  
HN58X2532@SOIC8 [CX1045]  
HN58X2564@SOIC8 [CX1045]  
M5L2732 [CX0001]  
M5M29KB331(AVP)@TSOP48 [CX1004]  
M5M29KE131BTP@TSOP52 [CX1009]  
M5M29KT331(AVP)@TSOP48 [CX1004]  
M6MG3B641S16TP@TSOP52 [CX1009]  
M6MGB166S4B(WG)@FBGA72 [CX5001]  
M6MGB321S8TP@TSOP52 [CX1009]  
M6MGB32BS8WG@CSP66 [CX5001]  
M6MGB33BS8AWG@CSP66 [CX5001]  
M6MGB641S4TP@TSOP52 [CX1009]  
M6MGB647M34CKT@TSOP52 [CX1009]  
M6MGB64BM34CDG@CSP88 [CX5053]  
M6MGB64BS4WG@CSP67 [CX5001]  
M6MGD137W33(WG)@CSP72 [CX5053]  
M6MGE157S4KT@TSOP52 [CX1009]  
M6MGT321S4TP@TSOP52 [CX1009]  
M6MGT32BS4WG@CSP66 [CX5001]  
M6MGT331S8KT@TSOP52 [CX1009]  
M6MGT641S16TP@TSOP52 [CX1009]  
M6MGT641S8TP@TSOP52 [CX1009]  
M6MGT64BM17AWG@CSP67 [CX5053]  
M6MGT64BM34CWG@CSP67 [CX5053]  
M6MGT64BS8WG@CSP67 [CX5001]  
MC10256@BGA208 [CX5226#1]  
R1EX24002A@TSSOP8 [CX1059]  
R1EX24004A@TSSOP8 [CX1059]  
R1EX24008A@TSSOP8 [CX1059]  
R1EX24016A@TSSOP8 [CX1059]  
R1EX24032A@TSSOP8 [CX1059]  
R1EX24064A@TSSOP8 [CX1059]  
R1EX24128A@TSSOP8 [CX1059]  
R1EX24256A@TSSOP8 [CX1059]  
R1EX24512A@TSSOP8 [CX1059]  
R1EX25002A@TSSOP8 [CX1059]  
R1EX25004A@TSSOP8 [CX1059]

R1EX25008A@SOIC8 [CX1045]  
R1EX25016A@SOIC8 [CX1045]  
R1EX25032A@SOIC8 [CX1045]  
R1EX25064A@SOIC8 [CX1045]

R1EX25008A@TSSOP8 [CX1059]  
R1EX25016A@TSSOP8 [CX1059]  
R1EX25032A@TSSOP8 [CX1059]  
R1EX25064A@TSSOP8 [CX1059]

#### DRAM & SRAM

R1LV0408C@SOP32 [CX1020]  
R1LV0408C@TSOP32 [CX1002]

R1LV0408C@STSOP32 [CX1003]

#### MICROCONTROLLER

HD6473032F@QFP80 [CX3018]  
HD6473334YCP@PLCC84 [CX2084]  
HD6473334YTF@QFP80 [CX3016]  
HD6473337YCP@PLCC84 [CX2084]  
HD6473644RH@QFP64 [CX3014]  
HD64738024H@QFP80 [CX3018]  
HD6475368CG@PLCC84 [CX2084]  
HD6475368F@QFP80 [CX3018]  
HD6475368RCP@PLCC84 [CX2084]  
HD6475368SCG@PLCC84 [CX2084]  
HD6475368SF@QFP80 [CX3018]  
HD64F2110BTE@QFP100 [CX3021]  
HD64F2110BVTE@QFP100 [CX3021]  
HD64F2132RTF10@QFP80 [CX3016]  
HD64F2132RVTF10@QFP80 [CX3016]  
HD64F2134ATF10@QFP80 [CX3016]  
HD64F2134AVTF10@QFP80 [CX3016]  
HD64F2134TF10@QFP80 [CX3016]  
HD64F2134VTF10@QFP80 [CX3016]  
HD64F2138ATF10@QFP80 [CX3016]  
HD64F2138AVTF10@QFP80 [CX3016]  
HD64F2138TF10@QFP80 [CX3016]  
HD64F2138VTF10@QFP80 [CX3016]  
HD64F2140BVTE10@QFP100 [CX3021]  
HD64F2141BVTE10@QFP100 [CX3021]  
HD64F2142RTE20@QFP100 [CX3021]  
HD64F2142RVTE10@QFP100 [CX3021]  
HD64F2144ATE20@QFP100 [CX3021]  
HD64F2144AVTE10@QFP100 [CX3021]  
HD64F2144TE20@QFP100 [CX3021]  
HD64F2144VTE10@QFP100 [CX3021]  
HD64F2145BVTE10@QFP100 [CX3021]  
HD64F2147ATE20@QFP100 [CX3021]  
HD64F2147AVTE10@QFP100 [CX3021]  
HD64F2147NTE20@QFP100 [CX3021]  
HD64F2147NVTE10@QFP100 [CX3021]  
HD64F2148ATE20@QFP100 [CX3021]  
HD64F2148AVTE10@QFP100 [CX3021]  
HD64F2148BTE20@QFP100 [CX3021]  
HD64F2148BVTE10@QFP100 [CX3021]  
HD64F2148TE20@QFP100 [CX3021]  
HD64F2148VTE10@QFP100 [CX3021]  
HD64F2149YTE20@QFP100 [CX3021]  
HD64F2149YVTE10@QFP100 [CX3021]  
HD64F2218UTF@QFP100 [CX3071]  
HD64F2238BF@PQFP100 [CX3022]

HD6473032TF@QFP80 [CX3016]  
HD6473334YF@QFP80 [CX3018]  
HD6473337YCG@PLCC84 [CX2084]  
HD6473644H@QFP64 [CX3014]  
HD64738024F@PQFP80 [CX3019]  
HD64738024W@QFP80 [CX3016]  
HD6475368CP@PLCC84 [CX2084]  
HD6475368RCG@PLCC84 [CX2084]  
HD6475368RF@QFP80 [CX3018]  
HD6475368SCP@PLCC84 [CX2084]  
HD64F2110BFA@QFP100 [CX3021]  
HD64F2110BVFA@QFP100 [CX3021]  
HD64F2132RFA20@QFP80 [CX3018]  
HD64F2132RVFA10@QFP80 [CX3018]  
HD64F2134AFA20@QFP80 [CX3018]  
HD64F2134AVFA10@QFP80 [CX3018]  
HD64F2134FA20@QFP80 [CX3018]  
HD64F2134VFA10@QFP80 [CX3018]  
HD64F2138AFA20@QFP80 [CX3018]  
HD64F2138AVFA10@QFP80 [CX3018]  
HD64F2138FA20@QFP80 [CX3018]  
HD64F2138VFA10@QFP80 [CX3018]  
HD64F2140BVFA10@QFP100 [CX3021]  
HD64F2141BVFA10@QFP100 [CX3021]  
HD64F2142RFA20@QFP100 [CX3021]  
HD64F2142RVFA10@QFP100 [CX3021]  
HD64F2144AFA20@QFP100 [CX3021]  
HD64F2144AVFA10@QFP100 [CX3021]  
HD64F2144FA20@QFP100 [CX3021]  
HD64F2144VFA10@QFP100 [CX3021]  
HD64F2145BVFA10@QFP100 [CX3021]  
HD64F2147AFA20@QFP100 [CX3021]  
HD64F2147AVFA10@QFP100 [CX3021]  
HD64F2147NFA20@QFP100 [CX3021]  
HD64F2147NVFA10@QFP100 [CX3021]  
HD64F2148AFA20@QFP100 [CX3021]  
HD64F2148AVFA10@QFP100 [CX3021]  
HD64F2148BFA20@QFP100 [CX3021]  
HD64F2148BVFA10@QFP100 [CX3021]  
HD64F2148FA20@QFP100 [CX3021]  
HD64F2148VFA10@QFP100 [CX3021]  
HD64F2149YFA20@QFP100 [CX3021]  
HD64F2149YVFA10@QFP100 [CX3021]  
HD64F2218TF@QFP100 [CX3071]  
HD64F2238ATE@TQFP100 [CX3043]  
HD64F2238BFA@QFP100 [CX3043]

HD64F2238BTE@TQFP100 [CX3043]	HD64F2238BTF@TQFP100 [CX3071]
HD64F2238RF@PQFP100 [CX3022]	HD64F2238RFA@QFP100 [CX3043]
HD64F2238RTE@TQFP100 [CX3043]	HD64F2238RTF@TQFP100 [CX3071]
HD64F2239F@PQFP100 [CX3022]	HD64F2239FA@QFP100 [CX3043]
HD64F2239TE@TQFP100 [CX3043]	HD64F2239TF@TQFP100 [CX3071]
HD64F2258F@PQFP100 [CX3022]	HD64F2258FA@QFP100 [CX3043]
HD64F2258TE@TQFP100 [CX3043]	HD64F2265FA@TQFP100 [CX3043]
HD64F2265TE@TQFP100 [CX3043]	HD64F2265TF@TQFP100 [CX3071]
HD64F2266FA@TQFP100 [CX3043]	HD64F2266TE@TQFP100 [CX3043]
HD64F2266TF@TQFP100 [CX3071]	HD64F2268FA@TQFP100 [CX3043]
HD64F2268TE@TQFP100 [CX3043]	HD64F2268TF@TQFP100 [CX3071]
HD64F2280F20B@QFP100 [CX3022]	HD64F2280F20RB@QFP100 [CX3022]
HD64F2282F20@QFP100 [CX3022]	HD64F2314VF@PQFP100 [CX3022]
HD64F2314VTE@QFP100 [CX3043]	HD64F2315VF@PQFP100 [CX3022]
HD64F2315VTE@QFP100 [CX3043]	HD64F2317VF@PQFP100 [CX3022]
HD64F2317VTE@QFP100 [CX3043]	HD64F2317VTF@QFP100 [CX3043]
HD64F2318VF@PQFP100 [CX3022]	HD64F2318VTE@QFP100 [CX3043]
HD64F2318VTF@QFP100 [CX3043]	HD64F2319EVF@PQFP100 [CX3022]
HD64F2319EVTE@QFP100 [CX3043]	HD64F2319VF@PQFP100 [CX3022]
HD64F2319VTE@QFP100 [CX3043]	HD64F2612FA20@QFP80 [CX3018]
HD64F2615F20@QFP80 [CX3018]	HD64F2615F24@QFP80 [CX3018]
HD64F3024F@TQFP100 [CX3021]	HD64F3024FP@PQFP100 [CX3022]
HD64F3024TE@TQFP100 [CX3021]	HD64F3026F@QFP100 [CX3021]
HD64F3026FP@PQFP100 [CX3022]	HD64F3026TE@TQFP100 [CX3021]
HD64F3029F@QFP100 [CX3043]	HD64F3029TE@TQFP100 [CX3043]
HD64F3039F@QFP80 [CX3018]	HD64F3039TE@TQFP80 [CX3016]
HD64F3039VF@QFP80 [CX3018]	HD64F3039VTE@TQFP80 [CX3016]
HD64F3048BF@TQFP100 [CX3021]	HD64F3048BTE@TQFP100 [CX3021]
HD64F3048BVF@TQFP100 [CX3021]	HD64F3048BVTE@TQFP100 [CX3021]
HD64F3048F@TQFP100 [CX3021]	HD64F3048TF@TQFP100 [CX3021]
HD64F3048VF@TQFP100 [CX3021]	HD64F3048VTF@TQFP100 [CX3021]
HD64F3052BF@TQFP100 [CX3021]	HD64F3052BTE@TQFP100 [CX3021]
HD64F3052BVF@TQFP100 [CX3021]	HD64F3052BVTE@TQFP100 [CX3021]
HD64F3052F@TQFP100 [CX3021]	HD64F3052TE@TQFP100 [CX3021]
HD64F3062BF@TQFP100 [CX3021]	HD64F3062BFP@PQFP100 [CX3022]
HD64F3062BTE@TQFP100 [CX3021]	HD64F3062F@TQFP100 [CX3021]
HD64F3062FP@PQFP100 [CX3022]	HD64F3062RF@TQFP100 [CX3021]
HD64F3062RFP@PQFP100 [CX3022]	HD64F3062RTE@TQFP100 [CX3021]
HD64F3062RVF@TQFP100 [CX3021]	HD64F3062RVFP@PQFP100 [CX3022]
HD64F3062RVTE@TQFP100 [CX3021]	HD64F3062TE@TQFP100 [CX3021]
HD64F3062VF@TQFP100 [CX3021]	HD64F3062VFP@TQFP100 [CX3022]
HD64F3062VTE@TQFP100 [CX3021]	HD64F3064BF@TQFP100 [CX3021]
HD64F3064BFP@PQFP100 [CX3022]	HD64F3064BTE@TQFP100 [CX3021]
HD64F3064F@TQFP100 [CX3021]	HD64F3064FP@PQFP100 [CX3022]
HD64F3064TE@TQFP100 [CX3021]	HD64F3067F@TQFP100 [CX3021]
HD64F3067FP@PQFP100 [CX3022]	HD64F3067RF@TQFP100 [CX3021]
HD64F3067RFP@PQFP100 [CX3022]	HD64F3067RTE@TQFP100 [CX3021]
HD64F3067RVF@TQFP100 [CX3021]	HD64F3067RVFP@PQFP100 [CX3022]
HD64F3067RVTE@TQFP100 [CX3021]	HD64F3067TE@TQFP100 [CX3021]
HD64F3067VF@TQFP100 [CX3021]	HD64F3067VFP@TQFP100 [CX3022]
HD64F3067VTE@TQFP100 [CX3021]	HD64F3068F@TQFP100 [CX3021]
HD64F3068TE@TQFP100 [CX3021]	HD64F3069F@TQFP100 [CX3043]
HD64F3069TE@TQFP100 [CX3043]	HD64F3334YCP@PLCC84 [CX2084]
HD64F3334YF@TQFP80 [CX3018]	HD64F3334YFLH@TQFP80 [CX3018]
HD64F3334YTF@TQFP80 [CX3016]	HD64F3334YTF@TQFP80 [CX3016]
HD64F3337YCP@PLCC84 [CX2084]	HD64F3337YF@TQFP80 [CX3018]
HD64F3337YFLH@TQFP80 [CX3018]	HD64F3337YTF@TQFP80 [CX3016]
HD64F3337YTF@TQFP80 [CX3016]	HD64F3394YCP@PLCC84 [CX2084]
HD64F3394YF@TQFP80 [CX3018]	HD64F3394YFLH@TQFP80 [CX3018]



HD64F3394YTF@TQFP80 [CX3016]  
HD64F3397CP@PLCC84 [CX2084]  
HD64F3397FLH@TQFP80 [CX3018]  
HD64F3397TFLH@TQFP80 [CX3016]  
HD64F3434FLH@TQFP100 [CX3021]  
HD64F3434TFLH@TQFP100 [CX3021]  
HD64F3437FLH@TQFP100 [CX3021]  
HD64F3437TFLH@TQFP100 [CX3021]  
HD64F36012FT@QFN48 [CX4021]  
HD64F36012FY@QFP48 [CX3007]  
HD64F36012GFT@QFN48 [CX4021]  
HD64F36012GFY@QFP48 [CX3007]  
HD64F36014FT@QFN48 [CX4021]  
HD64F36014FY@QFP48 [CX3007]  
HD64F36014GFT@QFN48 [CX4021]  
HD64F36014GFY@QFP48 [CX3007]  
HD64F36022FT@QFN48 [CX4021]  
HD64F36022FY@QFP48 [CX3007]  
HD64F36022GFT@QFN48 [CX4021]  
HD64F36022GFY@QFP48 [CX3007]  
HD64F36024FT@QFN48 [CX4021]  
HD64F36024FY@QFP48 [CX3007]  
HD64F36024GFT@QFN48 [CX4021]  
HD64F36024GFY@QFP48 [CX3007]  
HD64F36034GFZ@QFP64 [CX3011]  
HD64F36034H@QFP64 [CX3014]  
HD64F36037GFZ@QFP64 [CX3011]  
HD64F36037H@QFP64 [CX3014]  
HD64F36049H@QFP80 [CX3018]  
HD64F36054GFZ@QFP64 [CX3011]  
HD64F36054H@QFP64 [CX3014]  
HD64F36057GFZ@QFP64 [CX3011]  
HD64F36057H@QFP64 [CX3014]  
HD64F36064GFP@QFP64 [CX3011]  
HD64F36064H@QFP64 [CX3014]  
HD64F36074GFZW@QFP64 [CX3011]  
HD64F36074GHV@QFP64 [CX3014]  
HD64F36074GHZ@QFP64 [CX3014]  
HD64F36074LФЗ@QFP64 [CX3011]  
HD64F36074LH@QFP64 [CX3014]  
HD64F36074LHW@QFP64 [CX3014]  
HD64F36074LHZW@QFP64 [CX3014]  
HD64F36077GFZW@QFP64 [CX3011]  
HD64F36077GHV@QFP64 [CX3014]  
HD64F36077GHZ@QFP64 [CX3014]  
HD64F36077LФЗ@QFP64 [CX3011]  
HD64F36077LH@QFP64 [CX3014]  
HD64F36077LHW@QFP64 [CX3014]  
HD64F36077LHZW@QFP64 [CX3014]  
HD64F36078GFZW@QFP64 [CX3011]  
HD64F36078GHV@QFP64 [CX3014]  
HD64F36078GHZ@QFP64 [CX3014]  
HD64F36078LФЗ@QFP64 [CX3011]  
HD64F36078LH@QFP64 [CX3014]  
HD64F36078LHW@QFP64 [CX3014]  
HD64F36078LHZW@QFP64 [CX3014]  
HD64F36079GFZW@QFP64 [CX3011]  
HD64F36079GHV@QFP64 [CX3014]  
HD64F36079GHZ@QFP64 [CX3014]

HD64F3394YTFLH@TQFP80 [CX3016]  
HD64F3397F@TQFP80 [CX3018]  
HD64F3397TF@TQFP80 [CX3016]  
HD64F3434F@TQFP100 [CX3021]  
HD64F3434TF@TQFP100 [CX3021]  
HD64F3437F@TQFP100 [CX3021]  
HD64F3437TF@TQFP100 [CX3021]  
HD64F36012FPP@QFP64 [CX3011]  
HD64F36012FX@QFP48 [CX3008]  
HD64F36012GFP@QFP64 [CX3011]  
HD64F36012GFX@QFP48 [CX3008]  
HD64F36014FPP@QFP64 [CX3011]  
HD64F36014FX@QFP48 [CX3008]  
HD64F36014GFP@QFP64 [CX3011]  
HD64F36014GFX@QFP48 [CX3008]  
HD64F36022FPP@QFP64 [CX3011]  
HD64F36022FX@QFP48 [CX3008]  
HD64F36022GFP@QFP64 [CX3011]  
HD64F36022GFX@QFP48 [CX3008]  
HD64F36024FPP@QFP64 [CX3011]  
HD64F36024FX@QFP48 [CX3008]  
HD64F36024GFP@QFP64 [CX3011]  
HD64F36024GFX@QFP48 [CX3008]  
HD64F36034FZ@QFP64 [CX3011]  
HD64F36034GH@QFP64 [CX3014]  
HD64F36037FZ@QFP64 [CX3011]  
HD64F36037GH@QFP64 [CX3014]  
HD64F36049GH@QFP80 [CX3018]  
HD64F36054FZ@QFP64 [CX3011]  
HD64F36054GH@QFP64 [CX3014]  
HD64F36057FZ@QFP64 [CX3011]  
HD64F36057GH@QFP64 [CX3014]  
HD64F36064FPP@QFP64 [CX3011]  
HD64F36064GH@QFP64 [CX3014]  
HD64F36074GFZ@QFP64 [CX3011]  
HD64F36074GH@QFP64 [CX3014]  
HD64F36074GHW@QFP64 [CX3014]  
HD64F36074GHZW@QFP64 [CX3014]  
HD64F36074LHV@QFP64 [CX3014]  
HD64F36074LHZ@QFP64 [CX3014]  
HD64F36077GFZ@QFP64 [CX3011]  
HD64F36077GH@QFP64 [CX3014]  
HD64F36077GHW@QFP64 [CX3014]  
HD64F36077GHZW@QFP64 [CX3014]  
HD64F36077LФЗW@QFP64 [CX3011]  
HD64F36077LHV@QFP64 [CX3014]  
HD64F36077LHZ@QFP64 [CX3014]  
HD64F36078GFZ@QFP64 [CX3011]  
HD64F36078GH@QFP64 [CX3014]  
HD64F36078GHW@QFP64 [CX3014]  
HD64F36078GHZW@QFP64 [CX3014]  
HD64F36078LФЗW@QFP64 [CX3011]  
HD64F36078LHV@QFP64 [CX3014]  
HD64F36078LHZ@QFP64 [CX3014]  
HD64F36079GFZ@QFP64 [CX3011]  
HD64F36079GH@QFP64 [CX3014]  
HD64F36079GHW@QFP64 [CX3014]  
HD64F36079GHZW@QFP64 [CX3014]

HD64F36079LFZ@QFP64 [CX3011]  
HD64F36079LH@QFP64 [CX3014]  
HD64F36079LHW@QFP64 [CX3014]  
HD64F36079LHZ@QFP64 [CX3014]  
HD64F36087H@QFP64 [CX3014]  
HD64F36109GF@PQFP100 [CX3022]  
HD64F36109H@LQFP100 [CX3043]  
HD64F3642AP@SDIP64 [CX0064]  
HD64F3643H@TQFP64 [CX3014]  
HD64F3643W@TQFP80 [CX3016]  
HD64F3644P@SDIP64 [CX0064]  
HD64F3664BP@SDIP42 [CX0042]  
HD64F3664FX@QFP48 [CX3008]  
HD64F3664GBP@SDIP42 [CX0042]  
HD64F3664GFX@QFP48 [CX3008]  
HD64F3664GH@QFP64 [CX3014]  
HD64F3684FP@QFP64 [CX3011]  
HD64F3684GH@QFP64 [CX3014]  
HD64F3687FP@QFP64 [CX3011]  
HD64F3687GH@QFP64 [CX3014]  
HD64F3694FP@QFP64 [CX3011]  
HD64F3694FY@QFP48 [CX3007]  
HD64F3694GFX@QFP48 [CX3008]  
HD64F3694GH@QFP64 [CX3014]  
HD64F38002FP@TQFP64 [CX3011]  
HD64F38004FP@TQFP64 [CX3011]  
HD64F38024F@QFP80 [CX3019]  
HD64F38024RF@QFP80 [CX3019]  
HD64F38024RW@QFP80 [CX3016]  
HD64F38102FP@TQFP64 [CX3011]  
HD64F38104FP@TQFP64 [CX3011]  
HD64F38124D@QFP80 [CX3018]  
HD64F38124W@QFP80 [CX3016]  
HD64F38324H@QFP80 [CX3018]  
HD64F38324W@QFP80 [CX3016]  
HD64F38327H@QFP80 [CX3018]  
HD64F38327W@QFP80 [CX3016]  
HD64F38424H@QFP80 [CX3018]  
HD64F38424W@QFP80 [CX3016]  
HD64F38427H@QFP80 [CX3018]  
HD64F38427W@QFP80 [CX3016]  
HD64F39012FP@QFP64 [CX3011]  
HD64F39012FX@QFP48 [CX3008]  
HD64F39012GFP@QFP64 [CX3011]  
HD64F39012GFX@QFP48 [CX3008]  
HD64F39014FP@QFP64 [CX3011]  
HD64F39014FX@QFP48 [CX3008]  
HD64F39014GFP@QFP64 [CX3011]  
HD64F39014GFX@QFP48 [CX3008]  
HD64F39022FP@QFP64 [CX3011]  
HD64F39022FX@QFP48 [CX3008]  
HD64F39022GFP@QFP64 [CX3011]  
HD64F39022GFX@QFP48 [CX3008]  
HD64F39024FP@QFP64 [CX3011]  
HD64F39024FX@QFP48 [CX3008]  
HD64F39024GFP@QFP64 [CX3011]  
HD64F39024GFX@QFP48 [CX3008]  
HD64F7046F50@QFP80 [CX3018]  
HD64F7055F40@PQFP256(\*) [CX3070]

HD64F36079LFZW@QFP64 [CX3011]  
HD64F36079LHV@QFP64 [CX3014]  
HD64F36079LHZ@QFP64 [CX3014]  
HD64F36087FP@QFP64 [CX3011]  
HD64F36109F@PQFP100 [CX3022]  
HD64F36109GH@LQFP100 [CX3043]  
HD64F3642AH@TQFP64 [CX3014]  
HD64F3642AW@TQFP80 [CX3016]  
HD64F3643P@SDIP64 [CX0064]  
HD64F3644H@TQFP64 [CX3014]  
HD64F3644W@TQFP80 [CX3016]  
HD64F3664FP@QFP64 [CX3011]  
HD64F3664FY@QFP48 [CX3007]  
HD64F3664GFP@QFP64 [CX3011]  
HD64F3664GFY@QFP48 [CX3007]  
HD64F3664H@QFP64 [CX3014]  
HD64F3684GFP@QFP64 [CX3011]  
HD64F3684H@QFP64 [CX3014]  
HD64F3687GFP@QFP64 [CX3011]  
HD64F3687H@QFP64 [CX3014]  
HD64F3694FX@QFP48 [CX3008]  
HD64F3694GFP@QFP64 [CX3011]  
HD64F3694GFY@QFP48 [CX3007]  
HD64F3694H@QFP64 [CX3014]  
HD64F38002H@TQFP64 [CX3014]  
HD64F38004H@TQFP64 [CX3014]  
HD64F38024H@QFP80 [CX3018]  
HD64F38024RH@QFP80 [CX3018]  
HD64F38024W@QFP80 [CX3016]  
HD64F38102H@TQFP64 [CX3014]  
HD64F38104H@TQFP64 [CX3014]  
HD64F38124H@QFP80 [CX3018]  
HD64F38124WI@QFP80 [CX3016]  
HD64F38324HW@QFP80 [CX3018]  
HD64F38324WW@QFP80 [CX3016]  
HD64F38327HW@QFP80 [CX3018]  
HD64F38327WW@QFP80 [CX3016]  
HD64F38424HW@QFP80 [CX3018]  
HD64F38424WW@QFP80 [CX3016]  
HD64F38427HW@QFP80 [CX3018]  
HD64F38427WW@QFP80 [CX3016]  
HD64F39012FT@QFN48 [CX4021]  
HD64F39012FY@QFP48 [CX3007]  
HD64F39012GFT@QFN48 [CX4021]  
HD64F39012GFY@QFP48 [CX3007]  
HD64F39014FT@QFN48 [CX4021]  
HD64F39014FY@QFP48 [CX3007]  
HD64F39014GFT@QFN48 [CX4021]  
HD64F39014GFY@QFP48 [CX3007]  
HD64F39022FT@QFN48 [CX4021]  
HD64F39022FY@QFP48 [CX3007]  
HD64F39022GFT@QFN48 [CX4021]  
HD64F39022GFY@QFP48 [CX3007]  
HD64F39024FT@QFN48 [CX4021]  
HD64F39024FY@QFP48 [CX3007]  
HD64F39024GFT@QFN48 [CX4021]  
HD64F39024GFY@QFP48 [CX3007]  
HD64F7047F50@QFP100 [CX3021]  
HD64F7058F80@PQFP256(\*) [CX3070]

M30260F3AGP@QFP48 [CX3007]  
M30260F3VGP@QFP48 [CX3007]  
M30260F6TGP@QFP48 [CX3007]  
M30260F8AGP@QFP48 [CX3007]  
M30260F8VGP@QFP48 [CX3007]  
M30262F4GP@QFP48 [CX3007]  
M30262F8GP@QFP48 [CX3007]  
M30263F6AFP@SSOP42 [CX1056]  
M30620FCAFP@PQFP100 [CX3022]  
M30620FCNFP@PQFP100 [CX3022]  
M30620FCPFP@PQFP100 [CX3022]  
M30620FCPGP@TQFP100 [CX3021]  
M30621FCPGP@TQFP100(S) [CX3018]  
M30622F8PFP@PQFP100(S) [CX3022]  
M30622F8PGP@TQFP100(S) [CX3021]  
M30624FGAGP@TQFP100 [CX3021]  
M30624FGMGP@TQFP100 [CX3021]  
M30624FGNGP@TQFP100 [CX3021]  
M30624FGPFP@PQFP100(S) [CX3022]  
M30624FGPGP@TQFP100(S) [CX3021]  
M30626FHPFP@PQFP100(S) [CX3022]  
M30626FHPGP@TQFP100(S) [CX3021]  
M30626FJFP@PQFP100(S) [CX3022]  
M30626FJPGP@PQFP100(S) [CX3021]  
M3062AFCTFP@PQFP100(S) [CX3022]  
M3062AFCTGP@PQFP100(S) [CX3021]  
M3062AFCVFP@PQFP100(S) [CX3022]  
M3062AFCVGP@PQFP100(S) [CX3021]  
M3062CF8TFP@PQFP100(S) [CX3022]  
M3062CF8TGP@PQFP100(S) [CX3021]  
M3062JFHTFP@PQFP100(S) [CX3022]  
M3062JFHTGP@PQFP100(S) [CX3021]  
M3062JFHVFP@PQFP100(S) [CX3022]  
M3062JFHVGP@PQFP100(S) [CX3021]  
M3062LFGPFP@PQFP100(S) [CX3022]  
M3062LFGPGP@TQFP100(S) [CX3021]  
M306N4FCGP@QFP100 [CX3021]  
M306N4FCTGP@QFP100 [CX3021]  
M306N4FCVGP@QFP100 [CX3021]  
M306N4FGGP@QFP100 [CX3021]  
M306N4FGTGP@QFP100 [CX3021]  
M306N4FGVGP@QFP100 [CX3021]  
M306N5FCGP@QFP100 [CX3021]  
M306N5FCTGP@QFP100 [CX3021]  
M306N5FCVGP@QFP100 [CX3021]  
M306NBFCTFP@PQFP100 [CX3022]  
M306NKFHTGP@QFP100 [CX3021]  
M306NKFJGP@QFP100 [CX3021]  
M306NKFJVGP@QFP100 [CX3021]  
M306NLFHTGP@QFP100 [CX3021]  
M306NLFJGP@QFP100 [CX3021]  
M306NLFJVGP@QFP100 [CX3021]  
M30833FJGP@TQFP100 [CX3021]  
M30873FHGP@TQFP100 [CX3021]  
M30879FKGP@TQFP100 [CX3021]  
M30879FLGP@TQFP100 [CX3021]  
M34286G2GP [CX1067]  
M34508G4GP [CX1067]  
M34508G4HGP [CX1067]

M30260F3TGP@QFP48 [CX3007]  
M30260F6AGP@QFP48 [CX3007]  
M30260F6VGP@QFP48 [CX3007]  
M30260F8TGP@QFP48 [CX3007]  
M30262F3GP@QFP48 [CX3007]  
M30262F6GP@QFP48 [CX3007]  
M30263F3AFP@SSOP42 [CX1056]  
M30263F8AFP@SSOP42 [CX1056]  
M30620FCAGP@TQFP100 [CX3021]  
M30620FCNGP@TQFP100 [CX3021]  
M30620FCPFP@PQFP100(S) [CX3022]  
M30620FCPGP@TQFP100(S) [CX3021]  
M30622F8PFP@PQFP100 [CX3022]  
M30622F8PGP@TQFP100 [CX3021]  
M30624FGAFP@PQFP100 [CX3022]  
M30624FGMFP@PQFP100 [CX3022]  
M30624FGNFP@PQFP100 [CX3022]  
M30624FGPFP@PQFP100 [CX3022]  
M30624FGPGP@TQFP100 [CX3021]  
M30626FHPFP@PQFP100 [CX3022]  
M30626FHPGP@TQFP100 [CX3021]  
M30626FJFP@PQFP100 [CX3022]  
M30626FJPGP@PQFP100 [CX3021]  
M3062AFCTFP@PQFP100 [CX3022]  
M3062AFCTGP@PQFP100 [CX3021]  
M3062AFCVFP@PQFP100 [CX3022]  
M3062AFCVGP@PQFP100 [CX3021]  
M3062CF8TFP@PQFP100 [CX3022]  
M3062CF8TGP@PQFP100 [CX3021]  
M3062JFHTFP@PQFP100 [CX3022]  
M3062JFHTGP@PQFP100 [CX3021]  
M3062JFHVFP@PQFP100 [CX3022]  
M3062JFHVGP@PQFP100 [CX3021]  
M3062LFGPFP@PQFP100 [CX3022]  
M3062LFGPGP@TQFP100 [CX3021]  
M306N4FCFP@PQFP100 [CX3022]  
M306N4FCTFP@PQFP100 [CX3022]  
M306N4FCVFP@PQFP100 [CX3022]  
M306N4FGFP@PQFP100 [CX3022]  
M306N4FGTFP@PQFP100 [CX3022]  
M306N4FGVFP@PQFP100 [CX3022]  
M306N5FCFP@PQFP100 [CX3022]  
M306N5FCTFP@PQFP100 [CX3022]  
M306N5FCVFP@PQFP100 [CX3022]  
M306NAFGTFP@PQFP100 [CX3022]  
M306NKFHGP@QFP100 [CX3021]  
M306NKFHVGP@QFP100 [CX3021]  
M306NKFJTGP@QFP100 [CX3021]  
M306NLFHGP@QFP100 [CX3021]  
M306NLFHVGP@QFP100 [CX3021]  
M306NLFJTGP@QFP100 [CX3021]  
M30833FJFP@PQFP100 [CX3022]  
M30833FJTGP@TQFP100 [CX3021]  
M30876FJGP@TQFP100 [CX3021]  
M30879FLFP@TQFP100 [CX3022]  
M34283G2GP [CX1067]  
M34508G4FP [CX1031]  
M34508G4HFP [CX1031]  
M34509G4FP [CX1047]

M34509G4HFP [CX1047]  
M3455AG8FPP@QFP52 [CX3010]  
M37544G2(GP)@LQFP32 [CX3001]  
M37544G2A(GP)@LQFP32 [CX3001]  
M37545G4(FP)@SSOP36 [CX1046]  
M37545G6(FP)@SSOP36 [CX1046]  
M37545G8(FP)@SSOP36 [CX1046]  
M37546G2(FP)@SSOP36 [CX1046]  
M37546G2(SP)@SDIP32 [CX0032]  
M37546G4(GP)@LQFP32 [CX3001]  
M37547G2(FP)@SSOP36 [CX1046]  
M37548G1(FP)@TSSOP20 [CX1000]  
M37548G3(FP)@TSSOP20 [CX1000]  
M37549G1SP@SDIP24 [CX0032]  
M37549G2SP@SDIP24 [CX0032]  
M37549G3SP@SDIP24 [CX0032]  
M38039FFHHP@QFP64 [CX3011]  
M38039FFHSP@SDIP64 [CX0064]  
M38234G4(HP)@TQFP80 [CX3016]  
M38235G6(HP)@TQFP80 [CX3016]  
M38238G8(HP)@TQFP80 [CX3016]  
M38239GC(HP)@TQFP80 [CX3016]  
M3823AGF(HP)@TQFP80 [CX3016]  
M38503G4A(SP)@SDIP42 [CX0042]  
M38507F8SP@SDIP42 [CX0042]  
M38588G6(SP)@SDIP42 [CX0042]  
M38588G8(SP)@SDIP42 [CX0042]  
M38588GC(SP)@SDIP42 [CX0042]  
M38D24G4(FP)@QFP64 [CX3013]  
M38D24G6(FP)@QFP64 [CX3013]  
M38D28G8(FP)@QFP64 [CX3013]  
M38D29FF(HP)@QFP64 [CX3011]  
M38D29GC(HP)@QFP64 [CX3011]  
M38D29GF(HP)@QFP64 [CX3011]  
M38D58G8HP@QFP80 [CX3016]  
M38D59FFHP@QFP80 [CX3016]  
M38D59GCHP@QFP80 [CX3016]  
M38D59GFHP@QFP80 [CX3016]  
M3NN00FETGP@QFP100(S) [CX3021]  
R4F20102DFB [CX3014-1]  
R4F20102NFB [CX3014-1]  
R4F20102RDFB [CX3014-1]  
R4F20102RNFB [CX3014-1]  
R4F20103DFB [CX3014-1]  
R4F20103NFB [CX3014-1]  
R4F20103RDFB [CX3014-1]  
R4F20103RNFB [CX3014-1]  
R4F20114DFB [CX3014-1]  
R4F20114NFB [CX3014-1]  
R4F20114RDFB [CX3014-1]  
R4F20114RNFB [CX3014-1]  
R4F20115DFB [CX3014-1]  
R4F20115NFB [CX3014-1]  
R4F20115RDFB [CX3014-1]  
R4F20115RNFB [CX3014-1]  
R4F20202DFD [CX3018-1]  
R4F20202NFD [CX3018-1]  
R4F20202RDFD [CX3018-1]  
R4F20202RNFD [CX3018-1]

M34559G6FPP@QFP52 [CX3010]  
M3455AGCFPP@QFP52 [CX3010]  
M37544G2(SP)@SDIP32 [CX0032]  
M37544G2A(SP)@SDIP32 [CX0032]  
M37545G4(GP)@LQFP32 [CX3001]  
M37545G6(GP)@LQFP32 [CX3001]  
M37545G8(GP)@LQFP32 [CX3001]  
M37546G2(GP)@LQFP32 [CX3001]  
M37546G4(FP)@SSOP36 [CX1046]  
M37546G4(SP)@SDIP32 [CX0032]  
M37547G4(FP)@SSOP36 [CX1046]  
M37548G2(FP)@TSSOP20 [CX1000]  
M37549G1FPP@SSOP24 [CX1047]  
M37549G2FPP@SSOP24 [CX1047]  
M37549G3FPP@SSOP24 [CX1047]  
M38039FFHFP@QFP64 [CX3044]  
M38039FFHHP@QFP64 [CX3044]  
M38234G4(FP)@PQFP80 [CX3020]  
M38235G6(FP)@PQFP80 [CX3020]  
M38238G8(FP)@PQFP80 [CX3020]  
M38239GC(FP)@PQFP80 [CX3020]  
M3823AGF(FP)@PQFP80 [CX3020]  
M38503G4A(FP)@SSOP42 [CX1046]  
M38507F8FPP@SSOP42 [CX1056]  
M38588G6(FP)@SSOP42 [CX1046]  
M38588G8(FP)@SSOP42 [CX1046]  
M38588GC(FP)@SSOP42 [CX1046]  
M38859FFHHP@QFP80 [CX3016]  
M38D24G4(HP)@QFP64 [CX3011]  
M38D24G6(HP)@QFP64 [CX3011]  
M38D28G8(HP)@QFP64 [CX3011]  
M38D29GC(FP)@QFP64 [CX3013]  
M38D29GF(FP)@QFP64 [CX3013]  
M38D58G8FPP@PQFP80 [CX3020]  
M38D59FFFPP@PQFP80 [CX3020]  
M38D59GCFPP@PQFP80 [CX3020]  
M38D59GFFPP@PQFP80 [CX3020]  
M3NN00FETGP@QFP100 [CX3021]  
R4F20102DFA [CX3011-3]  
R4F20102NFA [CX3011-3]  
R4F20102RDFA [CX3011-3]  
R4F20102RNFA [CX3011-3]  
R4F20103DFA [CX3011-3]  
R4F20103NFA [CX3011-3]  
R4F20103RDFA [CX3011-3]  
R4F20103RNFA [CX3011-3]  
R4F20114DFA [CX3011-3]  
R4F20114NFA [CX3011-3]  
R4F20114RDFA [CX3011-3]  
R4F20114RNFA [CX3011-3]  
R4F20115DFA [CX3011-3]  
R4F20115NFA [CX3011-3]  
R4F20115RDFA [CX3011-3]  
R4F20115RNFA [CX3011-3]  
R4F20202DFC [CX3016-1]  
R4F20202NFC [CX3016-1]  
R4F20202RDFC [CX3016-1]  
R4F20202RNFC [CX3016-1]  
R4F20203DFC [CX3016-1]

R4F20203DFD [CX3018-1]	R4F20203NFC [CX3016-1]
R4F20203NFD [CX3018-1]	R4F20203RDFC [CX3016-1]
R4F20203RDFD [CX3018-1]	R4F20203RNFC [CX3016-1]
R4F20203RNFD [CX3018-1]	R4F20214DFC [CX3016-1]
R4F20214DFD [CX3018-1]	R4F20214NFC [CX3016-1]
R4F20214NFD [CX3018-1]	R4F20214RDFC [CX3016-1]
R4F20214RDFD [CX3018-1]	R4F20214RNFC [CX3016-1]
R4F20214RNFD [CX3018-1]	R4F20215DFC [CX3016-1]
R4F20215DFD [CX3018-1]	R4F20215NFC [CX3016-1]
R4F20215NFD [CX3018-1]	R4F20215RDFC [CX3016-1]
R4F20215RDFD [CX3018-1]	R4F20215RNFC [CX3016-1]
R4F20215RNFD [CX3018-1]	R4F20222DFC [CX3016-1]
R4F20222DFD [CX3018-1]	R4F20222NFC [CX3016-1]
R4F20222NFD [CX3018-1]	R4F20222RDFC [CX3016-1]
R4F20222RDFD [CX3018-1]	R4F20222RNFC [CX3016-1]
R4F20222RNFD [CX3018-1]	R4F20223DFC [CX3016-1]
R4F20223DFD [CX3018-1]	R4F20223NFC [CX3016-1]
R4F20223NFD [CX3018-1]	R4F20223RDFC [CX3016-1]
R4F20223RDFD [CX3018-1]	R4F20223RNFC [CX3016-1]
R4F20223RNFD [CX3018-1]	R4F20234DFC [CX3016-1]
R4F20234DFD [CX3018-1]	R4F20234NFC [CX3016-1]
R4F20234NFD [CX3018-1]	R4F20234RDFC [CX3016-1]
R4F20234RDFD [CX3018-1]	R4F20234RNFC [CX3016-1]
R4F20234RNFD [CX3018-1]	R4F20235DFC [CX3016-1]
R4F20235DFD [CX3018-1]	R4F20235NFC [CX3016-1]
R4F20235NFD [CX3018-1]	R4F20235RDFC [CX3016-1]
R4F20235RDFD [CX3018-1]	R4F20235RNFC [CX3016-1]
R4F20235RNFD [CX3018-1]	R4F20322RDFE [CX3021-2]
R4F20322RNFE [CX3021-2]	R4F20323RDFE [CX3021-2]
R4F20323RNFE [CX3021-2]	R4F20334RDFE [CX3021-2]
R4F20334RNFE [CX3021-2]	R4F20335RDFE [CX3021-2]
R4F20335RNFE [CX3021-2]	R5F1006AASP [CX1026]
R5F1006ADSP [CX1026]	R5F1006CASP [CX1026]
R5F1006CDSP [CX1026]	R5F1006DASP [CX1026]
R5F1006DDSP [CX1026]	R5F1006EASP [CX1026]
R5F1006EDSP [CX1026]	R5F1006FASP [CX1026]
R5F1006FDSP [CX1026]	R5F1006GASP [CX1026]
R5F1006GDSP [CX1026]	R5F1006HASP [CX1026]
R5F1006HDSP [CX1026]	R5F1006JASP [CX1026]
R5F1006JDSP [CX1026]	R5F1006KASP [CX1026]
R5F1006KDSP [CX1026]	R5F1006LASP [CX1026]
R5F1006LDSP [CX1026]	R5F1007AANA [CX4012]
R5F1007ADNA [CX4012]	R5F1007CANA [CX4012]
R5F1007CDNA [CX4012]	R5F1007DANA [CX4012]
R5F1007DDNA [CX4012]	R5F1007EANA [CX4012]
R5F1007EDNA [CX4012]	R5F1007FANA [CX4012]
R5F1007FDNA [CX4012]	R5F1007GANA [CX4012]
R5F1007GDNA [CX4012]	R5F1007HANA [CX4012]
R5F1007HDNA [CX4012]	R5F1007JANA [CX4012]
R5F1007JDNA [CX4012]	R5F1007KANA [CX4012]
R5F1007KDNA [CX4012]	R5F1007LANA [CX4012]
R5F1007LDNA [CX4012]	R5F1008AALA [CX0001]
R5F1008ADLA [CX0001]	R5F1008CALA [CX0001]
R5F1008CDLA [CX0001]	R5F1008DALA [CX0001]
R5F1008DDLA [CX0001]	R5F1008EALA [CX0001]
R5F1008EDLA [CX0001]	R5F1008FALA [CX0001]
R5F1008FDLA [CX0001]	R5F1008GALA [CX0001]
R5F1008GDLA [CX0001]	R5F1008HALA [CX0001]
R5F1008HDLA [CX0001]	R5F1008JALA [CX0001]

R5F1008JDLA [CX0001]	R5F1008KALA [CX0001]
R5F1008KDLA [CX0001]	R5F1008LALA [CX0001]
R5F1008LDLA [CX0001]	R5F100AAASP [CX1026]
R5F100AADSP [CX1026]	R5F100ACASP [CX1026]
R5F100ACDSP [CX1026]	R5F100ADASP [CX1026]
R5F100ADDSP [CX1026]	R5F100AEASP [CX1026]
R5F100AEDSP [CX1026]	R5F100AFASP [CX1026]
R5F100AFDSP [CX1026]	R5F100AGASP [CX1026]
R5F100AGDSP [CX1026]	R5F100AHASP [CX1026]
R5F100AHDSP [CX1026]	R5F100AJASP [CX1026]
R5F100AJDSP [CX1026]	R5F100AKASP [CX1026]
R5F100AKDSP [CX1026]	R5F100ALASP [CX1026]
R5F100ALDSP [CX1026]	R5F100BAANA [CX4015]
R5F100BADNA [CX4015]	R5F100BCANA [CX4015]
R5F100BCDNA [CX4015]	R5F100BDANA [CX4015]
R5F100BDDNA [CX4015]	R5F100BEANA [CX4015]
R5F100BEDNA [CX4015]	R5F100BFANA [CX4015]
R5F100BFDNA [CX4015]	R5F100BGANA [CX4015]
R5F100BGDNA [CX4015]	R5F100BHANA [CX4015]
R5F100BHDNA [CX4015]	R5F100BJANA [CX4015]
R5F100BJDNA [CX4015]	R5F100BKANA [CX4015]
R5F100BKDNA [CX4015]	R5F100BLANA [CX4015]
R5F100BLDNA [CX4015]	R5F100CAALA [CX0001]
R5F100CADLA [CX0001]	R5F100CCALA [CX0001]
R5F100CCDLA [CX0001]	R5F100CDALA [CX0001]
R5F100CDDL [CX0001]	R5F100CEALA [CX0001]
R5F100CEDLA [CX0001]	R5F100CFALA [CX0001]
R5F100CFDLA [CX0001]	R5F100CGALA [CX0001]
R5F100CGDLA [CX0001]	R5F100CHALA [CX0001]
R5F100CHDLA [CX0001]	R5F100CJALA [CX0001]
R5F100CJDLA [CX0001]	R5F100CKALA [CX0001]
R5F100CKDLA [CX0001]	R5F100CLALA [CX0001]
R5F100CLDLA [CX0001]	R5F100EAANA [CX4017]
R5F100EADNA [CX4017]	R5F100ECANA [CX4017]
R5F100ECDNA [CX4017]	R5F100EDANA [CX4017]
R5F100EDDNA [CX4017]	R5F100EEANA [CX4017]
R5F100EEDNA [CX4017]	R5F100EFANA [CX4017]
R5F100EFDNA [CX4017]	R5F100EGANA [CX4017]
R5F100EGDNA [CX4017]	R5F100EHANA [CX4017]
R5F100EHDNA [CX4017]	R5F100EJANA [CX4017]
R5F100EJDNA [CX4017]	R5F100EKANA [CX4017]
R5F100EKDNA [CX4017]	R5F100ELANA [CX4017]
R5F100ELDNA [CX4017]	R5F100FAAFP [CX3005]
R5F100FADFP [CX3005]	R5F100FCAFP [CX3005]
R5F100FCDFP [CX3005]	R5F100FDAFP [CX3005]
R5F100FDDFP [CX3005]	R5F100FEAFP [CX3005]
R5F100FEDFP [CX3005]	R5F100FFAFP [CX3005]
R5F100FFDFP [CX3005]	R5F100FGAFP [CX3005]
R5F100FGDFP [CX3005]	R5F100FHAFP [CX3005]
R5F100FHDFP [CX3005]	R5F100FJAFP [CX3005]
R5F100FJDFP [CX3005]	R5F100FKAFP [CX3005]
R5F100FKDFP [CX3005]	R5F100FLAFP [CX3005]
R5F100FLDFP [CX3005]	R5F100GAAFB [CX3007]
R5F100GAANA [CX4021]	R5F100GADFB [CX3007]
R5F100GADNA [CX4021]	R5F100GCAFB [CX3007]
R5F100GCANA [CX4021]	R5F100GCDFB [CX3007]
R5F100GCDNA [CX4021]	R5F100GDAFB [CX3007]
R5F100GDANA [CX4021]	R5F100GDDFB [CX3007]
R5F100GDDNA [CX4021]	R5F100GEAFB [CX3007]

R5F100GEANA [CX4021]	R5F100GEDFB [CX3007]
R5F100GEDNA [CX4021]	R5F100GFAFB [CX3007]
R5F100GFANA [CX4021]	R5F100GFDFB [CX3007]
R5F100GFDNA [CX4021]	R5F100GGAFB [CX3007]
R5F100GGANA [CX4021]	R5F100GGDFB [CX3007]
R5F100GGDNA [CX4021]	R5F100GHAFB [CX3007]
R5F100GHANA [CX4021]	R5F100GHDFB [CX3007]
R5F100GHDNA [CX4021]	R5F100GJAFB [CX3007]
R5F100GJANA [CX4021]	R5F100GJDFB [CX3007]
R5F100GJDNA [CX4021]	R5F100GKAFB [CX3007]
R5F100GKANA [CX4021]	R5F100GKDFB [CX3007]
R5F100GKDNA [CX4021]	R5F100GLAFB [CX3007]
R5F100GLANA [CX4021]	R5F100GLDFB [CX3007]
R5F100GLDNA [CX4021]	R5F100JCAFA [CX3010]
R5F100JCDDFA [CX3010]	R5F100JDAFA [CX3010]
R5F100JDDFA [CX3010]	R5F100JEAFB [CX3010]
R5F100JEDFA [CX3010]	R5F100JFAFA [CX3010]
R5F100JFDFA [CX3010]	R5F100JGAFB [CX3010]
R5F100JGDFB [CX3010]	R5F100JHAFB [CX3010]
R5F100JHDFB [CX3010]	R5F100JJAFB [CX3010]
R5F100JJDFB [CX3010]	R5F100JKAFB [CX3010]
R5F100JKDFB [CX3010]	R5F100JLAFB [CX3010]
R5F100JLDFB [CX3010]	R5F100LCABG [CX0001]
R5F100LCAFA [CX3012]	R5F100LCAFB [CX3011]
R5F100LCAFC [CX3085]	R5F100LCDBG [CX0001]
R5F100LCDFA [CX3012]	R5F100LCDFB [CX3011]
R5F100LCDFC [CX3085]	R5F100LDABG [CX0001]
R5F100LDAFA [CX3012]	R5F100LDAFB [CX3011]
R5F100LDAFC [CX3085]	R5F100LDDBG [CX0001]
R5F100LDDFA [CX3012]	R5F100LDDFB [CX3011]
R5F100LDDFC [CX3085]	R5F100LEABG [CX0001]
R5F100LEAFA [CX3012]	R5F100LEAFB [CX3011]
R5F100LEAFC [CX3085]	R5F100LEDBG [CX0001]
R5F100LEDFA [CX3012]	R5F100LEDFB [CX3011]
R5F100LEDFC [CX3085]	R5F100LFABG [CX0001]
R5F100LFAFA [CX3012]	R5F100LFAFB [CX3011]
R5F100LFAFC [CX3085]	R5F100LFDBG [CX0001]
R5F100LFDDFA [CX3012]	R5F100LFDFB [CX3011]
R5F100LFDFC [CX3085]	R5F100LGABG [CX0001]
R5F100LGAFB [CX3012]	R5F100LGAFB [CX3011]
R5F100LGAFC [CX3085]	R5F100LGDBG [CX0001]
R5F100LGDFB [CX3012]	R5F100LGDFB [CX3011]
R5F100LGDFC [CX3085]	R5F100LHABG [CX0001]
R5F100LHAFA [CX3012]	R5F100LHAFB [CX3011]
R5F100LHAFC [CX3085]	R5F100LHDBG [CX0001]
R5F100LHDFB [CX3012]	R5F100LHDFB [CX3011]
R5F100LHDFC [CX3085]	R5F100LJABG [CX0001]
R5F100LJAFB [CX3012]	R5F100LJAFB [CX3011]
R5F100LJAFB [CX3085]	R5F100LJDBG [CX0001]
R5F100LJDFB [CX3012]	R5F100LJDFB [CX3011]
R5F100LJDFC [CX3085]	R5F100LKABG [CX0001]
R5F100LKAFB [CX3012]	R5F100LKAFB [CX3011]
R5F100LKAFB [CX3085]	R5F100LKDBG [CX0001]
R5F100LKDFB [CX3012]	R5F100LKDFB [CX3011]
R5F100LKDFC [CX3085]	R5F100LLABG [CX0001]
R5F100LLAFB [CX3012]	R5F100LLAFB [CX3011]
R5F100LLAFC [CX3085]	R5F100LLDBG [CX0001]
R5F100LLDFB [CX3012]	R5F100LLDFB [CX3011]
R5F100LLDFC [CX3085]	R5F100MCAFA [CX3017]

R5F100MCAFB [CX3016]	R5F100MCDFA [CX3017]
R5F100MCDFB [CX3016]	R5F100MDAFA [CX3017]
R5F100MDAFB [CX3016]	R5F100MDDFA [CX3017]
R5F100MDDFB [CX3016]	R5F100MEAFA [CX3017]
R5F100MEAFB [CX3016]	R5F100MEDFA [CX3017]
R5F100MEDFB [CX3016]	R5F100MFafa [CX3017]
R5F100MFAFB [CX3016]	R5F100MFDFA [CX3017]
R5F100MFDFB [CX3016]	R5F100MGafa [CX3017]
R5F100MGAFB [CX3016]	R5F100MGDFA [CX3017]
R5F100MGDFB [CX3016]	R5F100MHafa [CX3017]
R5F100MHAFB [CX3016]	R5F100MHDFA [CX3017]
R5F100MHDFB [CX3016]	R5F100MJafa [CX3017]
R5F100MJAFB [CX3016]	R5F100MJDFA [CX3017]
R5F100MJDFB [CX3016]	R5F100MKafa [CX3017]
R5F100MKAFB [CX3016]	R5F100MKDFA [CX3017]
R5F100MKDFB [CX3016]	R5F100MLafa [CX3017]
R5F100MLAFB [CX3016]	R5F100MLDFA [CX3017]
R5F100MLDFB [CX3016]	R5F100PCAFA [CX3062]
R5F100PCAFB [CX3021]	R5F100PCDFA [CX3062]
R5F100PCDFB [CX3021]	R5F100PDAFA [CX3062]
R5F100PDAFB [CX3021]	R5F100PDDFA [CX3062]
R5F100PDDFB [CX3021]	R5F100PEAFA [CX3062]
R5F100PEAFB [CX3021]	R5F100PEDFA [CX3062]
R5F100PEDFB [CX3021]	R5F100PFAFA [CX3062]
R5F100PFAFB [CX3021]	R5F100PFDFA [CX3062]
R5F100PFDFB [CX3021]	R5F100PGafa [CX3062]
R5F100PGAFB [CX3021]	R5F100PGDFA [CX3062]
R5F100PGDFB [CX3021]	R5F100PHAFA [CX3062]
R5F100PHAFB [CX3021]	R5F100PHDFA [CX3062]
R5F100PHDFB [CX3021]	R5F100PJafa [CX3062]
R5F100PJAFB [CX3021]	R5F100PJDFA [CX3062]
R5F100PJDFB [CX3021]	R5F100PKafa [CX3062]
R5F100PKAFB [CX3021]	R5F100PKDFA [CX3062]
R5F100PKDFB [CX3021]	R5F100PLafa [CX3062]
R5F100PLAFB [CX3021]	R5F100PLDFA [CX3062]
R5F100PLDFB [CX3021]	R5F100SCAFB [CX3031]
R5F100SCDFB [CX3031]	R5F100SDAFB [CX3031]
R5F100SDDFB [CX3031]	R5F100SEAFB [CX3031]
R5F100SEDFB [CX3031]	R5F100SFAFB [CX3031]
R5F100SFDFB [CX3031]	R5F100SGAFB [CX3031]
R5F100SGDFB [CX3031]	R5F100SHAFA [CX3031]
R5F100SHDFB [CX3031]	R5F100SJAFB [CX3031]
R5F100SJDFB [CX3031]	R5F100SKAFB [CX3031]
R5F100SKDFB [CX3031]	R5F100SLAFB [CX3031]
R5F100SLDFB [CX3031]	R5F1016AASP [CX1026]
R5F1016ADSP [CX1026]	R5F1016CASP [CX1026]
R5F1016CDSP [CX1026]	R5F1016DASP [CX1026]
R5F1016DDSP [CX1026]	R5F1016EASP [CX1026]
R5F1016EDSP [CX1026]	R5F1016FASP [CX1026]
R5F1016FDSP [CX1026]	R5F1016GASP [CX1026]
R5F1016GDSP [CX1026]	R5F1016HASP [CX1026]
R5F1016HDSP [CX1026]	R5F1016JASP [CX1026]
R5F1016JDSP [CX1026]	R5F1016KASP [CX1026]
R5F1016KDSP [CX1026]	R5F1016LASP [CX1026]
R5F1016LDSP [CX1026]	R5F1017AANA [CX4012]
R5F1017ADNA [CX4012]	R5F1017CANA [CX4012]
R5F1017CDNA [CX4012]	R5F1017DANA [CX4012]
R5F1017DDNA [CX4012]	R5F1017EANA [CX4012]
R5F1017EDNA [CX4012]	R5F1017FANA [CX4012]



R5F1017FDNA [CX4012]	R5F1017GANA [CX4012]
R5F1017GDNA [CX4012]	R5F1017HANA [CX4012]
R5F1017HDNA [CX4012]	R5F1017JANA [CX4012]
R5F1017JDNA [CX4012]	R5F1017KANA [CX4012]
R5F1017KDNA [CX4012]	R5F1017LANA [CX4012]
R5F1017LDNA [CX4012]	R5F1018AALA [CX0001]
R5F1018ADLA [CX0001]	R5F1018CALA [CX0001]
R5F1018CDLA [CX0001]	R5F1018DALA [CX0001]
R5F1018DDLA [CX0001]	R5F1018EALA [CX0001]
R5F1018EDLA [CX0001]	R5F1018FALA [CX0001]
R5F1018FDLA [CX0001]	R5F1018GALA [CX0001]
R5F1018GDLA [CX0001]	R5F1018HALA [CX0001]
R5F1018HDLA [CX0001]	R5F1018JALA [CX0001]
R5F1018JDLA [CX0001]	R5F1018KALA [CX0001]
R5F1018KDLA [CX0001]	R5F1018LALA [CX0001]
R5F1018LDLA [CX0001]	R5F101AAASP [CX1026]
R5F101AADSP [CX1026]	R5F101ACASP [CX1026]
R5F101ACDSP [CX1026]	R5F101ADASP [CX1026]
R5F101ADDSP [CX1026]	R5F101AEASP [CX1026]
R5F101AEDSP [CX1026]	R5F101AFASP [CX1026]
R5F101AFDSP [CX1026]	R5F101AGASP [CX1026]
R5F101AGDSP [CX1026]	R5F101AHASP [CX1026]
R5F101AHDSP [CX1026]	R5F101AJASP [CX1026]
R5F101AJDSP [CX1026]	R5F101AKASP [CX1026]
R5F101AKDSP [CX1026]	R5F101ALASP [CX1026]
R5F101ALDSP [CX1026]	R5F101BAANA [CX4015]
R5F101BADNA [CX4015]	R5F101BCANA [CX4015]
R5F101BCDNA [CX4015]	R5F101BDANA [CX4015]
R5F101BDDNA [CX4015]	R5F101BEANA [CX4015]
R5F101BEDNA [CX4015]	R5F101BFANA [CX4015]
R5F101BFDNA [CX4015]	R5F101BGANA [CX4015]
R5F101BGDNA [CX4015]	R5F101BHANA [CX4015]
R5F101BHDNA [CX4015]	R5F101BJANA [CX4015]
R5F101BJDNA [CX4015]	R5F101BKANA [CX4015]
R5F101BKDNA [CX4015]	R5F101BLANA [CX4015]
R5F101BLDNA [CX4015]	R5F101CAALA [CX0001]
R5F101CADLA [CX0001]	R5F101CCALA [CX0001]
R5F101CCDLA [CX0001]	R5F101CDALA [CX0001]
R5F101CDDLA [CX0001]	R5F101CEALA [CX0001]
R5F101CEDLA [CX0001]	R5F101CFALA [CX0001]
R5F101CFDLA [CX0001]	R5F101CGALA [CX0001]
R5F101CGDLA [CX0001]	R5F101CHALA [CX0001]
R5F101CHDLA [CX0001]	R5F101CJALA [CX0001]
R5F101CJDLA [CX0001]	R5F101CKALA [CX0001]
R5F101CKDLA [CX0001]	R5F101CLALA [CX0001]
R5F101CLDLA [CX0001]	R5F101EAANA [CX4017]
R5F101EADNA [CX4017]	R5F101ECANA [CX4017]
R5F101ECDNA [CX4017]	R5F101EDANA [CX4017]
R5F101EDDNA [CX4017]	R5F101EEANA [CX4017]
R5F101EEDNA [CX4017]	R5F101EFANA [CX4017]
R5F101EFDNA [CX4017]	R5F101EGANA [CX4017]
R5F101EGDNA [CX4017]	R5F101EHANA [CX4017]
R5F101EHDNA [CX4017]	R5F101EJANA [CX4017]
R5F101EJDNA [CX4017]	R5F101EKANA [CX4017]
R5F101EKDNA [CX4017]	R5F101ELANA [CX4017]
R5F101ELDNA [CX4017]	R5F101FAAFP [CX3005]
R5F101FADFP [CX3005]	R5F101FCAFP [CX3005]
R5F101FCDFP [CX3005]	R5F101FDAFP [CX3005]
R5F101FDDFP [CX3005]	R5F101FEAFP [CX3005]

R5F101FEDFP [CX3005]	R5F101FFAFP [CX3005]
R5F101FFDFP [CX3005]	R5F101FGAFP [CX3005]
R5F101FGDFP [CX3005]	R5F101FHAFP [CX3005]
R5F101FHDFP [CX3005]	R5F101FJAFP [CX3005]
R5F101FJDFP [CX3005]	R5F101FKAFP [CX3005]
R5F101FKDFP [CX3005]	R5F101FLAFP [CX3005]
R5F101FLDFP [CX3005]	R5F101GAAFB [CX3007]
R5F101GAANA [CX4021]	R5F101GADFB [CX3007]
R5F101GADNA [CX4021]	R5F101GCAFB [CX3007]
R5F101GCANA [CX4021]	R5F101GCDFB [CX3007]
R5F101GCDNA [CX4021]	R5F101GDAFB [CX3007]
R5F101GDANA [CX4021]	R5F101GDDFB [CX3007]
R5F101GDDNA [CX4021]	R5F101GEAFB [CX3007]
R5F101GEANA [CX4021]	R5F101GEDFB [CX3007]
R5F101GEDNA [CX4021]	R5F101GFAFB [CX3007]
R5F101GFANA [CX4021]	R5F101GFDFB [CX3007]
R5F101GFDNA [CX4021]	R5F101GGAFB [CX3007]
R5F101GGANA [CX4021]	R5F101GGDFB [CX3007]
R5F101GGDNA [CX4021]	R5F101GHAFB [CX3007]
R5F101GHANA [CX4021]	R5F101GHDFB [CX3007]
R5F101GHDNA [CX4021]	R5F101GJAFB [CX3007]
R5F101GJANA [CX4021]	R5F101GJDFB [CX3007]
R5F101GJDNA [CX4021]	R5F101GKAFB [CX3007]
R5F101GKANA [CX4021]	R5F101GKDFB [CX3007]
R5F101GKDNA [CX4021]	R5F101GLAFB [CX3007]
R5F101GLANA [CX4021]	R5F101GLDFB [CX3007]
R5F101GLDNA [CX4021]	R5F101JCAFA [CX3010]
R5F101JCDFB [CX3010]	R5F101JDAFA [CX3010]
R5F101JDDFA [CX3010]	R5F101JEAFB [CX3010]
R5F101JEDFA [CX3010]	R5F101JFAFA [CX3010]
R5F101JFDFA [CX3010]	R5F101JGAFA [CX3010]
R5F101JGDFB [CX3010]	R5F101JHAFA [CX3010]
R5F101JHDFB [CX3010]	R5F101JJFAFA [CX3010]
R5F101JJDFB [CX3010]	R5F101JKAFB [CX3010]
R5F101JKDFB [CX3010]	R5F101JLAFA [CX3010]
R5F101JLDFB [CX3010]	R5F101LCABG [CX0001]
R5F101LCAFA [CX3011]	R5F101LCAFB [CX3011]
R5F101LCAFC [CX3011]	R5F101LCDBG [CX0001]
R5F101LCDFA [CX3011]	R5F101LCDFB [CX3011]
R5F101LCDFC [CX3011]	R5F101LDABG [CX0001]
R5F101LDAFA [CX3011]	R5F101LDAFB [CX3011]
R5F101LDAFC [CX3011]	R5F101LDDBG [CX0001]
R5F101LDDFA [CX3011]	R5F101LDDFB [CX3011]
R5F101LDDFC [CX3011]	R5F101LEABG [CX0001]
R5F101LEAFA [CX3011]	R5F101LEAFB [CX3011]
R5F101LEAFC [CX3011]	R5F101LEDBG [CX0001]
R5F101LEDFA [CX3011]	R5F101LEDFB [CX3011]
R5F101LEDFC [CX3011]	R5F101LFABG [CX0001]
R5F101LFAFA [CX3011]	R5F101LFAFB [CX3011]
R5F101LFAFC [CX3011]	R5F101LFDBG [CX0001]
R5F101LFDFA [CX3011]	R5F101LFDFB [CX3011]
R5F101LFDFC [CX3011]	R5F101LGABG [CX0001]
R5F101LGAFB [CX3011]	R5F101LGAFB [CX3011]
R5F101LGAFC [CX3011]	R5F101LGDBG [CX0001]
R5F101LGDFB [CX3011]	R5F101LGDFB [CX3011]
R5F101LGDFC [CX3011]	R5F101LHABG [CX0001]
R5F101LHAFA [CX3011]	R5F101LHAFB [CX3011]
R5F101LHAFC [CX3011]	R5F101LHDBG [CX0001]
R5F101LHDFB [CX3011]	R5F101LHDFB [CX3011]

R5F101LHDFC [CX3011]	R5F101LJABG [CX0001]
R5F101LJAFA [CX3011]	R5F101LJAFA [CX3011]
R5F101LJAFC [CX3011]	R5F101LJDBG [CX0001]
R5F101LJDFA [CX3011]	R5F101LJDFB [CX3011]
R5F101LJDFC [CX3011]	R5F101LKABG [CX0001]
R5F101LKAFB [CX3011]	R5F101LKAFB [CX3011]
R5F101LKAFB [CX3011]	R5F101LKDBG [CX0001]
R5F101LKDFB [CX3011]	R5F101LKDFB [CX3011]
R5F101LKDFC [CX3011]	R5F101LLABG [CX0001]
R5F101LLAFA [CX3011]	R5F101LLAFB [CX3011]
R5F101LLAFC [CX3011]	R5F101LLDBG [CX0001]
R5F101LLDFB [CX3011]	R5F101LLDFB [CX3011]
R5F101LLDFC [CX3011]	R5F101MCAFA [CX3017]
R5F101MCAFB [CX3016]	R5F101MCDFA [CX3017]
R5F101MCDFB [CX3016]	R5F101MDAFA [CX3017]
R5F101MDAFB [CX3016]	R5F101MDDFB [CX3017]
R5F101MDDFB [CX3016]	R5F101MEAFB [CX3017]
R5F101MEAFB [CX3016]	R5F101MEDFA [CX3017]
R5F101MEDFB [CX3016]	R5F101MFAFA [CX3017]
R5F101MFAFB [CX3016]	R5F101MFDFA [CX3017]
R5F101MFDFB [CX3016]	R5F101MGAFB [CX3017]
R5F101MGAFB [CX3016]	R5F101MGDFB [CX3017]
R5F101MGDFB [CX3016]	R5F101MHAFB [CX3017]
R5F101MHAFB [CX3016]	R5F101MHDFA [CX3017]
R5F101MHDFA [CX3016]	R5F101MJAFB [CX3017]
R5F101MJAFB [CX3016]	R5F101MJDFB [CX3017]
R5F101MJDFB [CX3016]	R5F101MKAFB [CX3017]
R5F101MKAFB [CX3016]	R5F101MKDFB [CX3017]
R5F101MKDFB [CX3016]	R5F101MLAFA [CX3017]
R5F101MLAFA [CX3016]	R5F101MLDFB [CX3017]
R5F101MLDFB [CX3016]	R5F101PCAFA [CX3062]
R5F101PCAFA [CX3021]	R5F101PCDFA [CX3062]
R5F101PCDFB [CX3021]	R5F101PDAFA [CX3062]
R5F101PDAFB [CX3021]	R5F101PDDFA [CX3062]
R5F101PDDFB [CX3021]	R5F101PEAFB [CX3062]
R5F101PEAFB [CX3021]	R5F101PEDFA [CX3062]
R5F101PEDFB [CX3021]	R5F101PFAFA [CX3062]
R5F101PFAFB [CX3021]	R5F101PFDFB [CX3062]
R5F101PFDFB [CX3021]	R5F101PGAFB [CX3062]
R5F101PGAFB [CX3021]	R5F101PGDFB [CX3062]
R5F101PGDFB [CX3021]	R5F101PHAFA [CX3062]
R5F101PHAFA [CX3021]	R5F101PHDFA [CX3062]
R5F101PHDFA [CX3021]	R5F101PJAFB [CX3062]
R5F101PJAFB [CX3021]	R5F101PJDFB [CX3062]
R5F101PJDFB [CX3021]	R5F101PKAFB [CX3062]
R5F101PKAFB [CX3021]	R5F101PKDFB [CX3062]
R5F101PKDFB [CX3021]	R5F101PLAFA [CX3062]
R5F101PLAFA [CX3021]	R5F101PLDFB [CX3062]
R5F101PLDFB [CX3021]	R5F101SCAFB [CX3031]
R5F101SCDFB [CX3031]	R5F101SDAFB [CX3031]
R5F101SDDFB [CX3031]	R5F101SEAFB [CX3031]
R5F101SEDFB [CX3031]	R5F101SFAFB [CX3031]
R5F101SFDFB [CX3031]	R5F101SGAFB [CX3031]
R5F101SGDFB [CX3031]	R5F101SHAFB [CX3031]
R5F101SHDFB [CX3031]	R5F101SJAFB [CX3031]
R5F101SJDFB [CX3031]	R5F101SKAFB [CX3031]
R5F101SKDFB [CX3031]	R5F101SLAFB [CX3031]
R5F101SLDFB [CX3031]	R5F10266ASP [CX1001]
R5F10266DSP [CX1001]	R5F10267ASP [CX1001]

R5F10267DSP [CX1001] R5F10268ASP [CX1001]  
R5F10268DSP [CX1001] R5F10269ASP [CX1001]  
R5F10269DSP [CX1001] R5F1026AASP [CX1001]  
R5F1026ADSP [CX1001] R5F10276ANA [CX4012]  
R5F10276DNA [CX4012] R5F10277ANA [CX4012]  
R5F10277DNA [CX4012] R5F10278ANA [CX4012]  
R5F10278DNA [CX4012] R5F10279ANA [CX4012]  
R5F10279DNA [CX4012] R5F1027AANA [CX4012]  
R5F1027ADNA [CX4012] R5F102A6ASP [CX1026]  
R5F102A6DSP [CX1026] R5F102A7ASP [CX1026]  
R5F102A7DSP [CX1026] R5F102A8ASP [CX1026]  
R5F102A8DSP [CX1026] R5F102A9ASP [CX1026]  
R5F102A9DSP [CX1026] R5F102AAASP [CX1026]  
R5F102AADSP [CX1026] R5F10366ASP [CX1001]  
R5F10366DSP [CX1001] R5F10367ASP [CX1001]  
R5F10367DSP [CX1001] R5F10368ASP [CX1001]  
R5F10368DSP [CX1001] R5F10369ASP [CX1001]  
R5F10369DSP [CX1001] R5F1036AASP [CX1001]  
R5F1036ADSP [CX1001] R5F10376ANA [CX4012]  
R5F10376DNA [CX4012] R5F10377ANA [CX4012]  
R5F10377DNA [CX4012] R5F10378ANA [CX4012]  
R5F10378DNA [CX4012] R5F10379ANA [CX4012]  
R5F10379DNA [CX4012] R5F1037AANA [CX4012]  
R5F1037ADNA [CX4012] R5F103A6ASP [CX1026]  
R5F103A6DSP [CX1026] R5F103A7ASP [CX1026]  
R5F103A7DSP [CX1026] R5F103A8ASP [CX1026]  
R5F103A8DSP [CX1026] R5F103A9ASP [CX1026]  
R5F103A9DSP [CX1026] R5F103AAASP [CX1026]  
R5F103AADSP [CX1026] R5F10Y14ASP [CX1001]  
R5F10Y16ASP [CX1001] R5F10Y17ASP [CX1001]  
R5F10Y44ASP [CX1001] R5F10Y46ASP [CX1001]  
R5F10Y47ASP [CX1001] R5F21102DFP@TQFP32 [CX3001]  
R5F21102FP@TQFP32 [CX3001] R5F21103DFP@TQFP32 [CX3001]  
R5F21103FP@TQFP32 [CX3001] R5F21104DFP@TQFP32 [CX3001]  
R5F21104FP@TQFP32 [CX3001] R5F21112DFP@TQFP32 [CX3001]  
R5F21112FP@TQFP32 [CX3001] R5F21113DFP@TQFP32 [CX3001]  
R5F21113FP@TQFP32 [CX3001] R5F21114DFP@TQFP32 [CX3001]  
R5F21114FP@TQFP32 [CX3001] R5F21122DFP@TQFP32 [CX3001]  
R5F21122FP@TQFP32 [CX3001] R5F21123DFP@TQFP32 [CX3001]  
R5F21123FP@TQFP32 [CX3001] R5F21124DFP@TQFP32 [CX3001]  
R5F21124FP@TQFP32 [CX3001] R5F21132DFP@TQFP32 [CX3001]  
R5F21132FP@TQFP32 [CX3001] R5F21133DFP@TQFP32 [CX3001]  
R5F21133FP@TQFP32 [CX3001] R5F21134DFP@TQFP32 [CX3001]  
R5F21134FP@TQFP32 [CX3001] R5F21142DSP@TSSOP20 [CX1000]  
R5F21142DSP@TSSOP20(single ISP) [CX0001]  
R5F21142DSP@TSSOP20(single wire) [CX1000]  
R5F21142DSP@TSSOP20(UART ISP) [CX0001]  
R5F21142DSP@TSSOP20(UART mode) [CX1000]  
R5F21142SP@TSSOP20 [CX1000]  
R5F21142SP@TSSOP20(single ISP) [CX0001]  
R5F21142SP@TSSOP20(single wire) [CX1000]  
R5F21142SP@TSSOP20(UART ISP) [CX0001]  
R5F21142SP@TSSOP20(UART mode) [CX1000]  
R5F21143DSP@TSSOP20 [CX1000]  
R5F21143DSP@TSSOP20(single ISP) [CX0001]  
R5F21143DSP@TSSOP20(single wire) [CX1000]  
R5F21143DSP@TSSOP20(UART ISP) [CX0001]  
R5F21143DSP@TSSOP20(UART mode) [CX1000]  
R5F21143SP@TSSOP20 [CX1000]

R5F21143SP@TSSOP20(single ISP) [CX0001]  
R5F21143SP@TSSOP20(single wire) [CX1000]  
R5F21143SP@TSSOP20(UART ISP) [CX0001]  
R5F21143SP@TSSOP20(UART mode) [CX1000]  
R5F21144DSP@TSSOP20 [CX1000]  
R5F21144DSP@TSSOP20(single ISP) [CX0001]  
R5F21144DSP@TSSOP20(single wire) [CX1000]  
R5F21144DSP@TSSOP20(UART ISP) [CX0001]  
R5F21144DSP@TSSOP20(UART mode) [CX1000]  
R5F21144SP@TSSOP20 [CX1000]  
R5F21144SP@TSSOP20(single ISP) [CX0001]  
R5F21144SP@TSSOP20(single wire) [CX1000]  
R5F21144SP@TSSOP20(UART ISP) [CX0001]  
R5F21144SP@TSSOP20(UART mode) [CX1000]  
R5F21152DSP@TSSOP20 [CX1000]  
R5F21152DSP@TSSOP20(single ISP) [CX0001]  
R5F21152DSP@TSSOP20(single wire) [CX1000]  
R5F21152DSP@TSSOP20(UART ISP) [CX0001]  
R5F21152DSP@TSSOP20(UART mode) [CX1000]  
R5F21152SP@TSSOP20 [CX1000]  
R5F21152SP@TSSOP20(single ISP) [CX0001]  
R5F21152SP@TSSOP20(single wire) [CX1000]  
R5F21152SP@TSSOP20(UART ISP) [CX0001]  
R5F21152SP@TSSOP20(UART mode) [CX1000]  
R5F21153DSP@TSSOP20 [CX1000]  
R5F21153DSP@TSSOP20(single ISP) [CX0001]  
R5F21153DSP@TSSOP20(single wire) [CX1000]  
R5F21153DSP@TSSOP20(UART ISP) [CX0001]  
R5F21153DSP@TSSOP20(UART mode) [CX1000]  
R5F21153SP@TSSOP20 [CX1000]  
R5F21153SP@TSSOP20(single ISP) [CX0001]  
R5F21153SP@TSSOP20(single wire) [CX1000]  
R5F21153SP@TSSOP20(UART ISP) [CX0001]  
R5F21153SP@TSSOP20(UART mode) [CX1000]  
R5F21154DSP@TSSOP20 [CX1000]  
R5F21154DSP@TSSOP20(single ISP) [CX0001]  
R5F21154DSP@TSSOP20(single wire) [CX1000]  
R5F21154DSP@TSSOP20(UART ISP) [CX0001]  
R5F21154DSP@TSSOP20(UART mode) [CX1000]  
R5F21154SP@TSSOP20 [CX1000]  
R5F21154SP@TSSOP20(single ISP) [CX0001]  
R5F21154SP@TSSOP20(single wire) [CX1000]  
R5F21154SP@TSSOP20(UART ISP) [CX0001]  
R5F21154SP@TSSOP20(UART mode) [CX1000]  
R5F21162DSP@TSSOP20 [CX1000]  
R5F21162DSP@TSSOP20(single ISP) [CX0001]  
R5F21162DSP@TSSOP20(single wire) [CX1000]  
R5F21162DSP@TSSOP20(UART ISP) [CX0001]  
R5F21162DSP@TSSOP20(UART mode) [CX1000]  
R5F21162SP@TSSOP20 [CX1000]  
R5F21162SP@TSSOP20(single ISP) [CX0001]  
R5F21162SP@TSSOP20(single wire) [CX1000]  
R5F21162SP@TSSOP20(UART ISP) [CX0001]  
R5F21162SP@TSSOP20(UART mode) [CX1000]  
R5F21163DSP@TSSOP20 [CX1000]  
R5F21163DSP@TSSOP20(single ISP) [CX0001]  
R5F21163DSP@TSSOP20(single wire) [CX1000]  
R5F21163DSP@TSSOP20(UART ISP) [CX0001]  
R5F21163DSP@TSSOP20(UART mode) [CX1000]

R5F21163SP@TSSOP20 [CX1000]  
R5F21163SP@TSSOP20(single ISP) [CX0001]  
R5F21163SP@TSSOP20(single wire) [CX1000]  
R5F21163SP@TSSOP20(UART ISP) [CX0001]  
R5F21163SP@TSSOP20(UART mode) [CX1000]  
R5F21164DSP@TSSOP20 [CX1000]  
R5F21164DSP@TSSOP20(single ISP) [CX0001]  
R5F21164DSP@TSSOP20(single wire) [CX1000]  
R5F21164DSP@TSSOP20(UART ISP) [CX0001]  
R5F21164DSP@TSSOP20(UART mode) [CX1000]  
R5F21164SP@TSSOP20 [CX1000]  
R5F21164SP@TSSOP20(single ISP) [CX0001]  
R5F21164SP@TSSOP20(single wire) [CX1000]  
R5F21164SP@TSSOP20(UART ISP) [CX0001]  
R5F21164SP@TSSOP20(UART mode) [CX1000]  
R5F21172DSP@TSSOP20 [CX1000]  
R5F21172DSP@TSSOP20(single ISP) [CX0001]  
R5F21172DSP@TSSOP20(single wire) [CX1000]  
R5F21172DSP@TSSOP20(UART ISP) [CX0001]  
R5F21172DSP@TSSOP20(UART mode) [CX1000]  
R5F21172SP@TSSOP20 [CX1000]  
R5F21172SP@TSSOP20(single ISP) [CX0001]  
R5F21172SP@TSSOP20(single wire) [CX1000]  
R5F21172SP@TSSOP20(UART ISP) [CX0001]  
R5F21172SP@TSSOP20(UART mode) [CX1000]  
R5F21173DSP@TSSOP20 [CX1000]  
R5F21173DSP@TSSOP20(single ISP) [CX0001]  
R5F21173DSP@TSSOP20(single wire) [CX1000]  
R5F21173DSP@TSSOP20(UART ISP) [CX0001]  
R5F21173DSP@TSSOP20(UART mode) [CX1000]  
R5F21173SP@TSSOP20 [CX1000]  
R5F21173SP@TSSOP20(single ISP) [CX0001]  
R5F21173SP@TSSOP20(single wire) [CX1000]  
R5F21173SP@TSSOP20(UART ISP) [CX0001]  
R5F21173SP@TSSOP20(UART mode) [CX1000]  
R5F21174DSP@TSSOP20 [CX1000]  
R5F21174DSP@TSSOP20(single ISP) [CX0001]  
R5F21174DSP@TSSOP20(single wire) [CX1000]  
R5F21174DSP@TSSOP20(UART ISP) [CX0001]  
R5F21174DSP@TSSOP20(UART mode) [CX1000]  
R5F21174SP@TSSOP20 [CX1000]  
R5F21174SP@TSSOP20(single ISP) [CX0001]  
R5F21174SP@TSSOP20(single wire) [CX1000]  
R5F21174SP@TSSOP20(UART ISP) [CX0001]  
R5F21174SP@TSSOP20(UART mode) [CX1000]  
R5F21181DD@SDIP20 [CX0032]  
R5F21181DD@SDIP20(single ISP) [CX0001]  
R5F21181DD@SDIP20(single wire) [CX0032]  
R5F21181DD@SDIP20(UART ISP) [CX0001]  
R5F21181DD@SDIP20(UART mode) [CX0032]  
R5F21181DSP@TSSOP20 [CX1000]  
R5F21181DSP@TSSOP20(single ISP) [CX0001]  
R5F21181DSP@TSSOP20(single wire) [CX1000]  
R5F21181DSP@TSSOP20(UART ISP) [CX0001]  
R5F21181DSP@TSSOP20(UART mode) [CX1000]  
R5F21181SP@TSSOP20 [CX1000]  
R5F21181SP@TSSOP20(single ISP) [CX0001]  
R5F21181SP@TSSOP20(single wire) [CX1000]  
R5F21181SP@TSSOP20(UART ISP) [CX0001]

R5F21181SP@TSSOP20(UART mode) [CX1000]  
R5F21182DD@SDIP20 [CX0032]  
R5F21182DD@SDIP20(single ISP) [CX0001]  
R5F21182DD@SDIP20(single wire) [CX0032]  
R5F21182DD@SDIP20(UART ISP) [CX0001]  
R5F21182DD@SDIP20(UART mode) [CX0032]  
R5F21182DSP@TSSOP20 [CX1000]  
R5F21182DSP@TSSOP20(single ISP) [CX0001]  
R5F21182DSP@TSSOP20(single wire) [CX1000]  
R5F21182DSP@TSSOP20(UART ISP) [CX0001]  
R5F21182DSP@TSSOP20(UART mode) [CX1000]  
R5F21182NP@QFN28 [CX4013]  
R5F21182NP@QFN28(single ISP) [CX0001]  
R5F21182NP@QFN28(single wire) [CX4013]  
R5F21182NP@QFN28(UART ISP) [CX0001]  
R5F21182NP@QFN28(UART mode) [CX4013]  
R5F21182SP@TSSOP20 [CX1000]  
R5F21182SP@TSSOP20(single ISP) [CX0001]  
R5F21182SP@TSSOP20(single wire) [CX1000]  
R5F21182SP@TSSOP20(UART ISP) [CX0001]  
R5F21182SP@TSSOP20(UART mode) [CX1000]  
R5F21183DD@SDIP20 [CX0032]  
R5F21183DD@SDIP20(single ISP) [CX0001]  
R5F21183DD@SDIP20(single wire) [CX0032]  
R5F21183DD@SDIP20(UART ISP) [CX0001]  
R5F21183DD@SDIP20(UART mode) [CX0032]  
R5F21183DSP@TSSOP20 [CX1000]  
R5F21183DSP@TSSOP20(single ISP) [CX0001]  
R5F21183DSP@TSSOP20(single wire) [CX1000]  
R5F21183DSP@TSSOP20(UART ISP) [CX0001]  
R5F21183DSP@TSSOP20(UART mode) [CX1000]  
R5F21183NP@QFN28 [CX4013]  
R5F21183NP@QFN28(single ISP) [CX0001]  
R5F21183NP@QFN28(single wire) [CX4013]  
R5F21183NP@QFN28(UART ISP) [CX0001]  
R5F21183NP@QFN28(UART mode) [CX4013]  
R5F21183SP@TSSOP20 [CX1000]  
R5F21183SP@TSSOP20(single ISP) [CX0001]  
R5F21183SP@TSSOP20(single wire) [CX1000]  
R5F21183SP@TSSOP20(UART ISP) [CX0001]  
R5F21183SP@TSSOP20(UART mode) [CX1000]  
R5F21184DD@SDIP20 [CX0032]  
R5F21184DD@SDIP20(single ISP) [CX0001]  
R5F21184DD@SDIP20(single wire) [CX0032]  
R5F21184DD@SDIP20(UART ISP) [CX0001]  
R5F21184DD@SDIP20(UART mode) [CX0032]  
R5F21184DSP@TSSOP20 [CX1000]  
R5F21184DSP@TSSOP20(single ISP) [CX0001]  
R5F21184DSP@TSSOP20(single wire) [CX1000]  
R5F21184DSP@TSSOP20(UART ISP) [CX0001]  
R5F21184DSP@TSSOP20(UART mode) [CX1000]  
R5F21184NP@QFN28 [CX4013]  
R5F21184NP@QFN28(single ISP) [CX0001]  
R5F21184NP@QFN28(single wire) [CX4013]  
R5F21184NP@QFN28(UART ISP) [CX0001]  
R5F21184NP@QFN28(UART mode) [CX4013]  
R5F21184SP@TSSOP20 [CX1000]  
R5F21184SP@TSSOP20(single ISP) [CX0001]  
R5F21184SP@TSSOP20(single wire) [CX1000]

R5F21184SP@TSSOP20(UART ISP) [CX0001]  
R5F21184SP@TSSOP20(UART mode) [CX1000]  
R5F21191DD@SDIP20 [CX0032]  
R5F21191DD@SDIP20(single ISP) [CX0001]  
R5F21191DD@SDIP20(single wire) [CX0032]  
R5F21191DD@SDIP20(UART ISP) [CX0001]  
R5F21191DD@SDIP20(UART mode) [CX0032]  
R5F21191DSP@TSSOP20 [CX1000]  
R5F21191DSP@TSSOP20(single ISP) [CX0001]  
R5F21191DSP@TSSOP20(single wire) [CX1000]  
R5F21191DSP@TSSOP20(UART ISP) [CX0001]  
R5F21191DSP@TSSOP20(UART mode) [CX1000]  
R5F21191SP@TSSOP20 [CX1000]  
R5F21191SP@TSSOP20(single ISP) [CX0001]  
R5F21191SP@TSSOP20(single wire) [CX1000]  
R5F21191SP@TSSOP20(UART ISP) [CX0001]  
R5F21191SP@TSSOP20(UART mode) [CX1000]  
R5F21192DD@SDIP20 [CX0032]  
R5F21192DD@SDIP20(single ISP) [CX0001]  
R5F21192DD@SDIP20(single wire) [CX0032]  
R5F21192DD@SDIP20(UART ISP) [CX0001]  
R5F21192DD@SDIP20(UART mode) [CX0032]  
R5F21192DSP@TSSOP20 [CX1000]  
R5F21192DSP@TSSOP20(single ISP) [CX0001]  
R5F21192DSP@TSSOP20(single wire) [CX1000]  
R5F21192DSP@TSSOP20(UART ISP) [CX0001]  
R5F21192DSP@TSSOP20(UART mode) [CX1000]  
R5F21192NP@QFN28 [CX4013]  
R5F21192NP@QFN28(single ISP) [CX0001]  
R5F21192NP@QFN28(single wire) [CX4013]  
R5F21192NP@QFN28(UART ISP) [CX0001]  
R5F21192NP@QFN28(UART mode) [CX4013]  
R5F21192SP@TSSOP20 [CX1000]  
R5F21192SP@TSSOP20(single ISP) [CX0001]  
R5F21192SP@TSSOP20(single wire) [CX1000]  
R5F21192SP@TSSOP20(UART ISP) [CX0001]  
R5F21192SP@TSSOP20(UART mode) [CX1000]  
R5F21193DD@SDIP20 [CX0032]  
R5F21193DD@SDIP20(single ISP) [CX0001]  
R5F21193DD@SDIP20(single wire) [CX0032]  
R5F21193DD@SDIP20(UART ISP) [CX0001]  
R5F21193DD@SDIP20(UART mode) [CX0032]  
R5F21193DSP@TSSOP20 [CX1000]  
R5F21193DSP@TSSOP20(single ISP) [CX0001]  
R5F21193DSP@TSSOP20(single wire) [CX1000]  
R5F21193DSP@TSSOP20(UART ISP) [CX0001]  
R5F21193DSP@TSSOP20(UART mode) [CX1000]  
R5F21193NP@QFN28 [CX4013]  
R5F21193NP@QFN28(single ISP) [CX0001]  
R5F21193NP@QFN28(single wire) [CX4013]  
R5F21193NP@QFN28(UART ISP) [CX0001]  
R5F21193NP@QFN28(UART mode) [CX4013]  
R5F21193SP@TSSOP20 [CX1000]  
R5F21193SP@TSSOP20(single ISP) [CX0001]  
R5F21193SP@TSSOP20(single wire) [CX1000]  
R5F21193SP@TSSOP20(UART ISP) [CX0001]  
R5F21193SP@TSSOP20(UART mode) [CX1000]  
R5F21194DD@SDIP20 [CX0032]  
R5F21194DD@SDIP20(single ISP) [CX0001]



R5F21194DD@SDIP20(single wire) [CX0032]  
R5F21194DD@SDIP20(UART ISP) [CX0001]  
R5F21194DD@SDIP20(UART mode) [CX0032]  
R5F21194DSP@TSSOP20 [CX1000]  
R5F21194DSP@TSSOP20(single ISP) [CX0001]  
R5F21194DSP@TSSOP20(single wire) [CX1000]  
R5F21194DSP@TSSOP20(UART ISP) [CX0001]  
R5F21194DSP@TSSOP20(UART mode) [CX1000]  
R5F21194NP@QFN28 [CX4013]  
R5F21194NP@QFN28(single ISP) [CX0001]  
R5F21194NP@QFN28(single wire) [CX4013]  
R5F21194NP@QFN28(UART ISP) [CX0001]  
R5F21194NP@QFN28(UART mode) [CX4013]  
R5F21194SP@TSSOP20 [CX1000]  
R5F21194SP@TSSOP20(single ISP) [CX0001]  
R5F21194SP@TSSOP20(single wire) [CX1000]  
R5F21194SP@TSSOP20(UART ISP) [CX0001]  
R5F21194SP@TSSOP20(UART mode) [CX1000]  
R5F211A1DD@SDIP20 [CX0032]  
R5F211A1DD@SDIP20(single ISP) [CX0001]  
R5F211A1DD@SDIP20(single wire) [CX0032]  
R5F211A1DD@SDIP20(UART ISP) [CX0001]  
R5F211A1DD@SDIP20(UART mode) [CX0032]  
R5F211A1DSP@TSSOP20 [CX1000]  
R5F211A1DSP@TSSOP20(single ISP) [CX0001]  
R5F211A1DSP@TSSOP20(single wire) [CX1000]  
R5F211A1DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A1DSP@TSSOP20(UART mode) [CX1000]  
R5F211A1SP@TSSOP20 [CX1000]  
R5F211A1SP@TSSOP20(single ISP) [CX0001]  
R5F211A1SP@TSSOP20(single wire) [CX1000]  
R5F211A1SP@TSSOP20(UART ISP) [CX0001]  
R5F211A1SP@TSSOP20(UART mode) [CX1000]  
R5F211A2DD@SDIP20 [CX0032]  
R5F211A2DD@SDIP20(single ISP) [CX0001]  
R5F211A2DD@SDIP20(single wire) [CX0032]  
R5F211A2DD@SDIP20(UART ISP) [CX0001]  
R5F211A2DD@SDIP20(UART mode) [CX0032]  
R5F211A2DSP@TSSOP20 [CX1000]  
R5F211A2DSP@TSSOP20(single ISP) [CX0001]  
R5F211A2DSP@TSSOP20(single wire) [CX1000]  
R5F211A2DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A2DSP@TSSOP20(UART mode) [CX1000]  
R5F211A2NP@QFN28 [CX4013]  
R5F211A2NP@QFN28(single ISP) [CX0001]  
R5F211A2NP@QFN28(single wire) [CX4013]  
R5F211A2NP@QFN28(UART ISP) [CX0001]  
R5F211A2NP@QFN28(UART mode) [CX4013]  
R5F211A2SP@TSSOP20 [CX1000]  
R5F211A2SP@TSSOP20(single ISP) [CX0001]  
R5F211A2SP@TSSOP20(single wire) [CX1000]  
R5F211A2SP@TSSOP20(UART ISP) [CX0001]  
R5F211A2SP@TSSOP20(UART mode) [CX1000]  
R5F211A3DD@SDIP20 [CX0032]  
R5F211A3DD@SDIP20(single ISP) [CX0001]  
R5F211A3DD@SDIP20(single wire) [CX0032]  
R5F211A3DD@SDIP20(UART ISP) [CX0001]  
R5F211A3DD@SDIP20(UART mode) [CX0032]  
R5F211A3DSP@TSSOP20 [CX1000]

R5F211A3DSP@TSSOP20(single ISP) [CX0001]  
R5F211A3DSP@TSSOP20(single wire) [CX1000]  
R5F211A3DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A3DSP@TSSOP20(UART mode) [CX1000]  
R5F211A3NP@QFN28 [CX4013]  
R5F211A3NP@QFN28(single ISP) [CX0001]  
R5F211A3NP@QFN28(single wire) [CX4013]  
R5F211A3NP@QFN28(UART ISP) [CX0001]  
R5F211A3NP@QFN28(UART mode) [CX4013]  
R5F211A3SP@TSSOP20 [CX1000]  
R5F211A3SP@TSSOP20(single ISP) [CX0001]  
R5F211A3SP@TSSOP20(single wire) [CX1000]  
R5F211A3SP@TSSOP20(UART ISP) [CX0001]  
R5F211A3SP@TSSOP20(UART mode) [CX1000]  
R5F211A4DD@SDIP20 [CX0032]  
R5F211A4DD@SDIP20(single ISP) [CX0001]  
R5F211A4DD@SDIP20(single wire) [CX0032]  
R5F211A4DD@SDIP20(UART ISP) [CX0001]  
R5F211A4DD@SDIP20(UART mode) [CX0032]  
R5F211A4DSP@TSSOP20 [CX1000]  
R5F211A4DSP@TSSOP20(single ISP) [CX0001]  
R5F211A4DSP@TSSOP20(single wire) [CX1000]  
R5F211A4DSP@TSSOP20(UART ISP) [CX0001]  
R5F211A4DSP@TSSOP20(UART mode) [CX1000]  
R5F211A4NP@QFN28 [CX4013]  
R5F211A4NP@QFN28(single ISP) [CX0001]  
R5F211A4NP@QFN28(single wire) [CX4013]  
R5F211A4NP@QFN28(UART ISP) [CX0001]  
R5F211A4NP@QFN28(UART mode) [CX4013]  
R5F211A4SP@TSSOP20 [CX1000]  
R5F211A4SP@TSSOP20(single ISP) [CX0001]  
R5F211A4SP@TSSOP20(single wire) [CX1000]  
R5F211A4SP@TSSOP20(UART ISP) [CX0001]  
R5F211A4SP@TSSOP20(UART mode) [CX1000]  
R5F211B1DD@SDIP20 [CX0032]  
R5F211B1DD@SDIP20(single ISP) [CX0001]  
R5F211B1DD@SDIP20(single wire) [CX0032]  
R5F211B1DD@SDIP20(UART ISP) [CX0001]  
R5F211B1DD@SDIP20(UART mode) [CX0032]  
R5F211B1DSP@TSSOP20 [CX1000]  
R5F211B1DSP@TSSOP20(single ISP) [CX0001]  
R5F211B1DSP@TSSOP20(single wire) [CX1000]  
R5F211B1DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B1DSP@TSSOP20(UART mode) [CX1000]  
R5F211B1SP@TSSOP20 [CX1000]  
R5F211B1SP@TSSOP20(single ISP) [CX0001]  
R5F211B1SP@TSSOP20(single wire) [CX1000]  
R5F211B1SP@TSSOP20(UART ISP) [CX0001]  
R5F211B1SP@TSSOP20(UART mode) [CX1000]  
R5F211B2DD@SDIP20 [CX0032]  
R5F211B2DD@SDIP20(single ISP) [CX0001]  
R5F211B2DD@SDIP20(single wire) [CX0032]  
R5F211B2DD@SDIP20(UART ISP) [CX0001]  
R5F211B2DD@SDIP20(UART mode) [CX0032]  
R5F211B2DSP@TSSOP20 [CX1000]  
R5F211B2DSP@TSSOP20(single ISP) [CX0001]  
R5F211B2DSP@TSSOP20(single wire) [CX1000]  
R5F211B2DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B2DSP@TSSOP20(UART mode) [CX1000]

R5F211B2NP@QFN28 [CX4013]  
R5F211B2NP@QFN28(single ISP) [CX0001]  
R5F211B2NP@QFN28(single wire) [CX4013]  
R5F211B2NP@QFN28(UART ISP) [CX0001]  
R5F211B2NP@QFN28(UART mode) [CX4013]  
R5F211B2SP@TSSOP20 [CX1000]  
R5F211B2SP@TSSOP20(single ISP) [CX0001]  
R5F211B2SP@TSSOP20(single wire) [CX1000]  
R5F211B2SP@TSSOP20(UART ISP) [CX0001]  
R5F211B2SP@TSSOP20(UART mode) [CX1000]  
R5F211B3DD@SDIP20 [CX0032]  
R5F211B3DD@SDIP20(single ISP) [CX0001]  
R5F211B3DD@SDIP20(single wire) [CX0032]  
R5F211B3DD@SDIP20(UART ISP) [CX0001]  
R5F211B3DD@SDIP20(UART mode) [CX0032]  
R5F211B3DSP@TSSOP20 [CX1000]  
R5F211B3DSP@TSSOP20(single ISP) [CX0001]  
R5F211B3DSP@TSSOP20(single wire) [CX1000]  
R5F211B3DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B3DSP@TSSOP20(UART mode) [CX1000]  
R5F211B3NP@QFN28 [CX4013]  
R5F211B3NP@QFN28(single ISP) [CX0001]  
R5F211B3NP@QFN28(single wire) [CX4013]  
R5F211B3NP@QFN28(UART ISP) [CX0001]  
R5F211B3NP@QFN28(UART mode) [CX4013]  
R5F211B3SP@TSSOP20 [CX1000]  
R5F211B3SP@TSSOP20(single ISP) [CX0001]  
R5F211B3SP@TSSOP20(single wire) [CX1000]  
R5F211B3SP@TSSOP20(UART ISP) [CX0001]  
R5F211B3SP@TSSOP20(UART mode) [CX1000]  
R5F211B4DD@SDIP20 [CX0032]  
R5F211B4DD@SDIP20(single ISP) [CX0001]  
R5F211B4DD@SDIP20(single wire) [CX0032]  
R5F211B4DD@SDIP20(UART ISP) [CX0001]  
R5F211B4DD@SDIP20(UART mode) [CX0032]  
R5F211B4DSP@TSSOP20 [CX1000]  
R5F211B4DSP@TSSOP20(single ISP) [CX0001]  
R5F211B4DSP@TSSOP20(single wire) [CX1000]  
R5F211B4DSP@TSSOP20(UART ISP) [CX0001]  
R5F211B4DSP@TSSOP20(UART mode) [CX1000]  
R5F211B4NP@QFN28 [CX4013]  
R5F211B4NP@QFN28(single ISP) [CX0001]  
R5F211B4NP@QFN28(single wire) [CX4013]  
R5F211B4NP@QFN28(UART ISP) [CX0001]  
R5F211B4NP@QFN28(UART mode) [CX4013]  
R5F211B4SP@TSSOP20 [CX1000]  
R5F211B4SP@TSSOP20(single ISP) [CX0001]  
R5F211B4SP@TSSOP20(single wire) [CX1000]  
R5F211B4SP@TSSOP20(UART ISP) [CX0001]  
R5F211B4SP@TSSOP20(UART mode) [CX1000]  
R5F21206JFP@TQFP48 [CX3007]  
R5F21206JFP@TQFP48(single ISP) [CX0001]  
R5F21206JFP@TQFP48(single wire) [CX3007]  
R5F21206KFP@TQFP48 [CX3007]  
R5F21206KFP@TQFP48(single ISP) [CX0001]  
R5F21206KFP@TQFP48(single wire) [CX3007]  
R5F21207JFP@TQFP48 [CX3007]  
R5F21207JFP@TQFP48(single ISP) [CX0001]  
R5F21207JFP@TQFP48(single wire) [CX3007]

R5F21207KFP@TQFP48 [CX3007]  
R5F21207KFP@TQFP48(single ISP) [CX0001]  
R5F21207KFP@TQFP48(single wire) [CX3007]  
R5F21208JFP@TQFP48 [CX3007]  
R5F21208JFP@TQFP48(single ISP) [CX0001]  
R5F21208JFP@TQFP48(single wire) [CX3007]  
R5F21208KFP@TQFP48 [CX3007]  
R5F21208KFP@TQFP48(single ISP) [CX0001]  
R5F21208KFP@TQFP48(single wire) [CX3007]  
R5F2120AJFP@TQFP48 [CX3007]  
R5F2120AJFP@TQFP48(single ISP) [CX0001]  
R5F2120AJFP@TQFP48(single wire) [CX3007]  
R5F2120AKFP@TQFP48 [CX3007]  
R5F2120AKFP@TQFP48(single ISP) [CX0001]  
R5F2120AKFP@TQFP48(single wire) [CX3007]  
R5F2120CJFP@TQFP48 [CX3007]  
R5F2120CJFP@TQFP48(single ISP) [CX0001]  
R5F2120CJFP@TQFP48(single wire) [CX3007]  
R5F2120CKFP@TQFP48 [CX3007]  
R5F2120CKFP@TQFP48(single ISP) [CX0001]  
R5F2120CKFP@TQFP48(single wire) [CX3007]  
R5F21216JFP@TQFP48 [CX3007]  
R5F21216JFP@TQFP48(single ISP) [CX0001]  
R5F21216JFP@TQFP48(single wire) [CX3007]  
R5F21216KFP@TQFP48 [CX3007]  
R5F21216KFP@TQFP48(single ISP) [CX0001]  
R5F21216KFP@TQFP48(single wire) [CX3007]  
R5F21217JFP@TQFP48 [CX3007]  
R5F21217JFP@TQFP48(single ISP) [CX0001]  
R5F21217JFP@TQFP48(single wire) [CX3007]  
R5F21217KFP@TQFP48 [CX3007]  
R5F21217KFP@TQFP48(single ISP) [CX0001]  
R5F21217KFP@TQFP48(single wire) [CX3007]  
R5F21218JFP@TQFP48 [CX3007]  
R5F21218JFP@TQFP48(single ISP) [CX0001]  
R5F21218JFP@TQFP48(single wire) [CX3007]  
R5F21218KFP@TQFP48 [CX3007]  
R5F21218KFP@TQFP48(single ISP) [CX0001]  
R5F21218KFP@TQFP48(single wire) [CX3007]  
R5F2121AJFP@TQFP48 [CX3007]  
R5F2121AJFP@TQFP48(single ISP) [CX0001]  
R5F2121AJFP@TQFP48(single wire) [CX3007]  
R5F2121AKFP@TQFP48 [CX3007]  
R5F2121AKFP@TQFP48(single ISP) [CX0001]  
R5F2121AKFP@TQFP48(single wire) [CX3007]  
R5F2121CJFP@TQFP48 [CX3007]  
R5F2121CJFP@TQFP48(single ISP) [CX0001]  
R5F2121CJFP@TQFP48(single wire) [CX3007]  
R5F2121CKFP@TQFP48 [CX3007]  
R5F2121CKFP@TQFP48(single ISP) [CX0001]  
R5F2121CKFP@TQFP48(single wire) [CX3007]  
R5F21226JFP@TQFP48 [CX3007]  
R5F21226JFP@TQFP48(single ISP) [CX0001]  
R5F21226JFP@TQFP48(single wire) [CX3007]  
R5F21226KFP@TQFP48 [CX3007]  
R5F21226KFP@TQFP48(single ISP) [CX0001]  
R5F21226KFP@TQFP48(single wire) [CX3007]  
R5F21227JFP@TQFP48 [CX3007]  
R5F21227JFP@TQFP48(single ISP) [CX0001]

R5F21227JFP@TQFP48(single wire) [CX3007]  
R5F21227KFP@TQFP48 [CX3007]  
R5F21227KFP@TQFP48(single ISP) [CX0001]  
R5F21227KFP@TQFP48(single wire) [CX3007]  
R5F21228JFP@TQFP48 [CX3007]  
R5F21228JFP@TQFP48(single ISP) [CX0001]  
R5F21228JFP@TQFP48(single wire) [CX3007]  
R5F21228KFP@TQFP48 [CX3007]  
R5F21228KFP@TQFP48(single ISP) [CX0001]  
R5F21228KFP@TQFP48(single wire) [CX3007]  
R5F2122AJFP@TQFP48 [CX3007]  
R5F2122AJFP@TQFP48(single ISP) [CX0001]  
R5F2122AJFP@TQFP48(single wire) [CX3007]  
R5F2122AKFP@TQFP48 [CX3007]  
R5F2122AKFP@TQFP48(single ISP) [CX0001]  
R5F2122AKFP@TQFP48(single wire) [CX3007]  
R5F2122CJFP@TQFP48 [CX3007]  
R5F2122CJFP@TQFP48(single ISP) [CX0001]  
R5F2122CJFP@TQFP48(single wire) [CX3007]  
R5F2122CKFP@TQFP48 [CX3007]  
R5F2122CKFP@TQFP48(single ISP) [CX0001]  
R5F2122CKFP@TQFP48(single wire) [CX3007]  
R5F21236DFP@TQFP48 [CX3007]  
R5F21236DFP@TQFP48(single wire) [CX3007]  
R5F21236JFP@TQFP48 [CX3007]  
R5F21236JFP@TQFP48(single ISP) [CX0001]  
R5F21236JFP@TQFP48(single wire) [CX3007]  
R5F21236KFP@TQFP48 [CX3007]  
R5F21236KFP@TQFP48(single ISP) [CX0001]  
R5F21236KFP@TQFP48(single wire) [CX3007]  
R5F21237JFP@TQFP48 [CX3007]  
R5F21237JFP@TQFP48(single ISP) [CX0001]  
R5F21237JFP@TQFP48(single wire) [CX3007]  
R5F21237KFP@TQFP48 [CX3007]  
R5F21237KFP@TQFP48(single ISP) [CX0001]  
R5F21237KFP@TQFP48(single wire) [CX3007]  
R5F21238JFP@TQFP48 [CX3007]  
R5F21238JFP@TQFP48(single ISP) [CX0001]  
R5F21238JFP@TQFP48(single wire) [CX3007]  
R5F21238KFP@TQFP48 [CX3007]  
R5F21238KFP@TQFP48(single ISP) [CX0001]  
R5F21238KFP@TQFP48(single wire) [CX3007]  
R5F2123AJFP@TQFP48 [CX3007]  
R5F2123AJFP@TQFP48(single ISP) [CX0001]  
R5F2123AJFP@TQFP48(single wire) [CX3007]  
R5F2123AKFP@TQFP48 [CX3007]  
R5F2123AKFP@TQFP48(single ISP) [CX0001]  
R5F2123AKFP@TQFP48(single wire) [CX3007]  
R5F2123CJFP@TQFP48 [CX3007]  
R5F2123CJFP@TQFP48(single ISP) [CX0001]  
R5F2123CJFP@TQFP48(single wire) [CX3007]  
R5F2123CKFP@TQFP48 [CX3007]  
R5F2123CKFP@TQFP48(single ISP) [CX0001]  
R5F2123CKFP@TQFP48(single wire) [CX3007]  
R5F21244SDFP@TQFP52 [CX3010]  
R5F21244SDFP@TQFP52(single ISP) [CX0001]  
R5F21244SDFP@TQFP52(single wire) [CX3010]  
R5F21244SDFP@TQFP52(UART ISP) [CX0001]  
R5F21244SDFP@TQFP52(UART mode) [CX3010]

R5F21244SNFP@TQFP52 [CX3010]  
R5F21244SNFP@TQFP52(single ISP) [CX0001]  
R5F21244SNFP@TQFP52(single wire) [CX3010]  
R5F21244SNFP@TQFP52(UART ISP) [CX0001]  
R5F21244SNFP@TQFP52(UART mode) [CX3010]  
R5F21245SDFP@TQFP52 [CX3010]  
R5F21245SDFP@TQFP52(single wire) [CX3010]  
R5F21245SDFP@TQFP52(UART ISP) [CX0001]  
R5F21245SDFP@TQFP52(UART mode) [CX3010]  
R5F21245SNFP@TQFP52 [CX3010]  
R5F21245SNFP@TQFP52(single wire) [CX3010]  
R5F21245SNFP@TQFP52(UART ISP) [CX0001]  
R5F21245SNFP@TQFP52(UART mode) [CX3010]  
R5F21246SDFP@TQFP52 [CX3010]  
R5F21246SDFP@TQFP52(single ISP) [CX0001]  
R5F21246SDFP@TQFP52(single wire) [CX3010]  
R5F21246SDFP@TQFP52(UART ISP) [CX0001]  
R5F21246SDFP@TQFP52(UART mode) [CX3010]  
R5F21246SNFP@TQFP52 [CX3010]  
R5F21246SNFP@TQFP52(single ISP) [CX0001]  
R5F21246SNFP@TQFP52(single wire) [CX3010]  
R5F21246SNFP@TQFP52(UART ISP) [CX0001]  
R5F21246SNFP@TQFP52(UART mode) [CX3010]  
R5F21247SDFP@TQFP52 [CX3010]  
R5F21247SDFP@TQFP52(single ISP) [CX0001]  
R5F21247SDFP@TQFP52(single wire) [CX3010]  
R5F21247SDFP@TQFP52(UART ISP) [CX0001]  
R5F21247SDFP@TQFP52(UART mode) [CX3010]  
R5F21247SNFP@TQFP52 [CX3010]  
R5F21247SNFP@TQFP52(single ISP) [CX0001]  
R5F21247SNFP@TQFP52(single wire) [CX3010]  
R5F21247SNFP@TQFP52(UART ISP) [CX0001]  
R5F21247SNFP@TQFP52(UART mode) [CX3010]  
R5F21248SDFP@TQFP52 [CX3010]  
R5F21248SDFP@TQFP52(single ISP) [CX0001]  
R5F21248SDFP@TQFP52(single wire) [CX3010]  
R5F21248SDFP@TQFP52(UART ISP) [CX0001]  
R5F21248SDFP@TQFP52(UART mode) [CX3010]  
R5F21248SNFP@TQFP52 [CX3010]  
R5F21248SNFP@TQFP52(single ISP) [CX0001]  
R5F21248SNFP@TQFP52(single wire) [CX3010]  
R5F21248SNFP@TQFP52(UART ISP) [CX0001]  
R5F21248SNFP@TQFP52(UART mode) [CX3010]  
R5F21254SDFP@TQFP52 [CX3010]  
R5F21254SDFP@TQFP52(single ISP) [CX0001]  
R5F21254SDFP@TQFP52(single wire) [CX3010]  
R5F21254SDFP@TQFP52(UART ISP) [CX0001]  
R5F21254SDFP@TQFP52(UART mode) [CX3010]  
R5F21254SNFP@TQFP52 [CX3010]  
R5F21254SNFP@TQFP52(single ISP) [CX0001]  
R5F21254SNFP@TQFP52(single wire) [CX3010]  
R5F21254SNFP@TQFP52(UART ISP) [CX0001]  
R5F21254SNFP@TQFP52(UART mode) [CX3010]  
R5F21255SDFP@TQFP52 [CX3010]  
R5F21255SDFP@TQFP52(single wire) [CX3010]  
R5F21255SDFP@TQFP52(UART mode) [CX3010]  
R5F21255SNFP@TQFP52 [CX3010]  
R5F21255SNFP@TQFP52(single wire) [CX3010]  
R5F21255SNFP@TQFP52(UART mode) [CX3010]

R5F21256SDFP@TQFP52 [CX3010]  
R5F21256SDFP@TQFP52(single ISP) [CX0001]  
R5F21256SDFP@TQFP52(single wire) [CX3010]  
R5F21256SDFP@TQFP52(UART ISP) [CX0001]  
R5F21256SDFP@TQFP52(UART mode) [CX3010]  
R5F21256SNFP@TQFP52 [CX3010]  
R5F21256SNFP@TQFP52(single ISP) [CX0001]  
R5F21256SNFP@TQFP52(single wire) [CX3010]  
R5F21256SNFP@TQFP52(UART ISP) [CX0001]  
R5F21256SNFP@TQFP52(UART mode) [CX3010]  
R5F21257SDFP@TQFP52 [CX3010]  
R5F21257SDFP@TQFP52(single ISP) [CX0001]  
R5F21257SDFP@TQFP52(single wire) [CX3010]  
R5F21257SDFP@TQFP52(UART ISP) [CX0001]  
R5F21257SDFP@TQFP52(UART mode) [CX3010]  
R5F21257SNFP@TQFP52 [CX3010]  
R5F21257SNFP@TQFP52(single ISP) [CX0001]  
R5F21257SNFP@TQFP52(single wire) [CX3010]  
R5F21257SNFP@TQFP52(UART ISP) [CX0001]  
R5F21257SNFP@TQFP52(UART mode) [CX3010]  
R5F21258SDFP@TQFP52 [CX3010]  
R5F21258SDFP@TQFP52(single ISP) [CX0001]  
R5F21258SDFP@TQFP52(single wire) [CX3010]  
R5F21258SDFP@TQFP52(UART ISP) [CX0001]  
R5F21258SDFP@TQFP52(UART mode) [CX3010]  
R5F21258SNFP@TQFP52 [CX3010]  
R5F21258SNFP@TQFP52(single ISP) [CX0001]  
R5F21258SNFP@TQFP52(single wire) [CX3010]  
R5F21258SNFP@TQFP52(UART ISP) [CX0001]  
R5F21258SNFP@TQFP52(UART mode) [CX3010]  
R5F21262DFP@QFP32 [CX3061]  
R5F21262DFP@QFP32(single ISP) [CX0001]  
R5F21262DFP@QFP32(single wire) [CX3061]  
R5F21262DFP@QFP32(UART ISP) [CX0001]  
R5F21262DFP@QFP32(UART mode) [CX3061]  
R5F21262JFP@QFP32 [CX3061]  
R5F21262JFP@QFP32(single ISP) [CX0001]  
R5F21262JFP@QFP32(single wire) [CX3061]  
R5F21262JFP@QFP32(UART ISP) [CX0001]  
R5F21262JFP@QFP32(UART mode) [CX3061]  
R5F21262KFP@QFP32 [CX3061]  
R5F21262KFP@QFP32(single ISP) [CX0001]  
R5F21262KFP@QFP32(single wire) [CX3061]  
R5F21262KFP@QFP32(UART ISP) [CX0001]  
R5F21262KFP@QFP32(UART mode) [CX3061]  
R5F21262NFP@QFP32 [CX3061]  
R5F21262NFP@QFP32(single ISP) [CX0001]  
R5F21262NFP@QFP32(single wire) [CX3061]  
R5F21262NFP@QFP32(UART ISP) [CX0001]  
R5F21262NFP@QFP32(UART mode) [CX3061]  
R5F21262SDFP@QFP32 [CX3061]  
R5F21262SDFP@QFP32(single ISP) [CX0001]  
R5F21262SDFP@QFP32(single wire) [CX3061]  
R5F21262SDFP@QFP32(UART ISP) [CX0001]  
R5F21262SDFP@QFP32(UART mode) [CX3061]  
R5F21262SJFP@QFP32 [CX3061]  
R5F21262SJFP@QFP32(single ISP) [CX0001]  
R5F21262SJFP@QFP32(single wire) [CX3061]  
R5F21262SJFP@QFP32(UART ISP) [CX0001]

R5F21262SJFP@QFP32(UART mode) [CX3061]  
R5F21262SKFP@QFP32 [CX3061]  
R5F21262SKFP@QFP32(single ISP) [CX0001]  
R5F21262SKFP@QFP32(single wire) [CX3061]  
R5F21262SKFP@QFP32(UART ISP) [CX0001]  
R5F21262SKFP@QFP32(UART mode) [CX3061]  
R5F21262SNFP@QFP32 [CX3061]  
R5F21262SNFP@QFP32(single ISP) [CX0001]  
R5F21262SNFP@QFP32(single wire) [CX3061]  
R5F21262SNFP@QFP32(UART ISP) [CX0001]  
R5F21262SNFP@QFP32(UART mode) [CX3061]  
R5F21264DFP@QFP32 [CX3061]  
R5F21264DFP@QFP32(single ISP) [CX0001]  
R5F21264DFP@QFP32(single wire) [CX3061]  
R5F21264DFP@QFP32(UART ISP) [CX0001]  
R5F21264DFP@QFP32(UART mode) [CX3061]  
R5F21264JFP@QFP32 [CX3061]  
R5F21264JFP@QFP32(single ISP) [CX0001]  
R5F21264JFP@QFP32(single wire) [CX3061]  
R5F21264JFP@QFP32(UART ISP) [CX0001]  
R5F21264JFP@QFP32(UART mode) [CX3061]  
R5F21264KFP@QFP32 [CX3061]  
R5F21264KFP@QFP32(single ISP) [CX0001]  
R5F21264KFP@QFP32(single wire) [CX3061]  
R5F21264KFP@QFP32(UART ISP) [CX0001]  
R5F21264KFP@QFP32(UART mode) [CX3061]  
R5F21264NFP@QFP32 [CX3061]  
R5F21264NFP@QFP32(single ISP) [CX0001]  
R5F21264NFP@QFP32(single wire) [CX3061]  
R5F21264NFP@QFP32(UART ISP) [CX0001]  
R5F21264NFP@QFP32(UART mode) [CX3061]  
R5F21264SDFP@QFP32 [CX3061]  
R5F21264SDFP@QFP32(single ISP) [CX0001]  
R5F21264SDFP@QFP32(single wire) [CX3061]  
R5F21264SDFP@QFP32(UART ISP) [CX0001]  
R5F21264SDFP@QFP32(UART mode) [CX3061]  
R5F21264SJFP@QFP32 [CX3061]  
R5F21264SJFP@QFP32(single ISP) [CX0001]  
R5F21264SJFP@QFP32(single wire) [CX3061]  
R5F21264SJFP@QFP32(UART ISP) [CX0001]  
R5F21264SJFP@QFP32(UART mode) [CX3061]  
R5F21264SKFP@QFP32 [CX3061]  
R5F21264SKFP@QFP32(single ISP) [CX0001]  
R5F21264SKFP@QFP32(single wire) [CX3061]  
R5F21264SKFP@QFP32(UART ISP) [CX0001]  
R5F21264SKFP@QFP32(UART mode) [CX3061]  
R5F21264SNFP@QFP32 [CX3061]  
R5F21264SNFP@QFP32(single ISP) [CX0001]  
R5F21264SNFP@QFP32(single wire) [CX3061]  
R5F21264SNFP@QFP32(UART ISP) [CX0001]  
R5F21264SNFP@QFP32(UART mode) [CX3061]  
R5F21265DFP@QFP32 [CX3061]  
R5F21265DFP@QFP32(single ISP) [CX0001]  
R5F21265DFP@QFP32(single wire) [CX3061]  
R5F21265DFP@QFP32(UART ISP) [CX0001]  
R5F21265DFP@QFP32(UART mode) [CX3061]  
R5F21265JFP@QFP32 [CX3061]  
R5F21265JFP@QFP32(single ISP) [CX0001]  
R5F21265JFP@QFP32(single wire) [CX3061]



R5F21265JFP@QFP32(UART ISP) [CX0001]  
R5F21265JFP@QFP32(UART mode) [CX3061]  
R5F21265KFP@QFP32 [CX3061]  
R5F21265KFP@QFP32(single ISP) [CX0001]  
R5F21265KFP@QFP32(single wire) [CX3061]  
R5F21265KFP@QFP32(UART ISP) [CX0001]  
R5F21265KFP@QFP32(UART mode) [CX3061]  
R5F21265NFP@QFP32 [CX3061]  
R5F21265NFP@QFP32(single ISP) [CX0001]  
R5F21265NFP@QFP32(single wire) [CX3061]  
R5F21265NFP@QFP32(UART ISP) [CX0001]  
R5F21265NFP@QFP32(UART mode) [CX3061]  
R5F21265SDFP@QFP32 [CX3061]  
R5F21265SDFP@QFP32(single ISP) [CX0001]  
R5F21265SDFP@QFP32(single wire) [CX3061]  
R5F21265SDFP@QFP32(UART ISP) [CX0001]  
R5F21265SDFP@QFP32(UART mode) [CX3061]  
R5F21265SJFP@QFP32 [CX3061]  
R5F21265SJFP@QFP32(single ISP) [CX0001]  
R5F21265SJFP@QFP32(single wire) [CX3061]  
R5F21265SJFP@QFP32(UART ISP) [CX0001]  
R5F21265SJFP@QFP32(UART mode) [CX3061]  
R5F21265SKFP@QFP32 [CX3061]  
R5F21265SKFP@QFP32(single ISP) [CX0001]  
R5F21265SKFP@QFP32(single wire) [CX3061]  
R5F21265SKFP@QFP32(UART ISP) [CX0001]  
R5F21265SKFP@QFP32(UART mode) [CX3061]  
R5F21265SNFP@QFP32 [CX3061]  
R5F21265SNFP@QFP32(single ISP) [CX0001]  
R5F21265SNFP@QFP32(single wire) [CX3061]  
R5F21265SNFP@QFP32(UART ISP) [CX0001]  
R5F21265SNFP@QFP32(UART mode) [CX3061]  
R5F21266DFP@QFP32 [CX3061]  
R5F21266DFP@QFP32(single ISP) [CX0001]  
R5F21266DFP@QFP32(single wire) [CX3061]  
R5F21266DFP@QFP32(UART ISP) [CX0001]  
R5F21266DFP@QFP32(UART mode) [CX3061]  
R5F21266JFP@QFP32 [CX3061]  
R5F21266JFP@QFP32(single ISP) [CX0001]  
R5F21266JFP@QFP32(single wire) [CX3061]  
R5F21266JFP@QFP32(UART ISP) [CX0001]  
R5F21266JFP@QFP32(UART mode) [CX3061]  
R5F21266KFP@QFP32 [CX3061]  
R5F21266KFP@QFP32(single ISP) [CX0001]  
R5F21266KFP@QFP32(single wire) [CX3061]  
R5F21266KFP@QFP32(UART ISP) [CX0001]  
R5F21266KFP@QFP32(UART mode) [CX3061]  
R5F21266NFP@QFP32 [CX3061]  
R5F21266NFP@QFP32(single ISP) [CX0001]  
R5F21266NFP@QFP32(single wire) [CX3061]  
R5F21266NFP@QFP32(UART ISP) [CX0001]  
R5F21266NFP@QFP32(UART mode) [CX3061]  
R5F21266SDFP@QFP32 [CX3061]  
R5F21266SDFP@QFP32(single ISP) [CX0001]  
R5F21266SDFP@QFP32(single wire) [CX3061]  
R5F21266SDFP@QFP32(UART ISP) [CX0001]  
R5F21266SDFP@QFP32(UART mode) [CX3061]  
R5F21266SJFP@QFP32 [CX3061]  
R5F21266SJFP@QFP32(single ISP) [CX0001]

R5F21266SJFP@QFP32(single wire) [CX3061]  
R5F21266SJFP@QFP32(UART ISP) [CX0001]  
R5F21266SJFP@QFP32(UART mode) [CX3061]  
R5F21266SKFP@QFP32 [CX3061]  
R5F21266SKFP@QFP32(single ISP) [CX0001]  
R5F21266SKFP@QFP32(single wire) [CX3061]  
R5F21266SKFP@QFP32(UART ISP) [CX0001]  
R5F21266SKFP@QFP32(UART mode) [CX3061]  
R5F21266SNFP@QFP32 [CX3061]  
R5F21266SNFP@QFP32(single ISP) [CX0001]  
R5F21266SNFP@QFP32(single wire) [CX3061]  
R5F21266SNFP@QFP32(UART ISP) [CX0001]  
R5F21266SNFP@QFP32(UART mode) [CX3061]  
R5F21272DFP@QFP32 [CX3061]  
R5F21272DFP@QFP32(single ISP) [CX0001]  
R5F21272DFP@QFP32(single wire) [CX3061]  
R5F21272DFP@QFP32(UART ISP) [CX0001]  
R5F21272DFP@QFP32(UART mode) [CX3061]  
R5F21272JFP@QFP32 [CX3061]  
R5F21272JFP@QFP32(single ISP) [CX0001]  
R5F21272JFP@QFP32(single wire) [CX3061]  
R5F21272JFP@QFP32(UART ISP) [CX0001]  
R5F21272JFP@QFP32(UART mode) [CX3061]  
R5F21272KFP@QFP32 [CX3061]  
R5F21272KFP@QFP32(single ISP) [CX0001]  
R5F21272KFP@QFP32(single wire) [CX3061]  
R5F21272KFP@QFP32(UART ISP) [CX0001]  
R5F21272KFP@QFP32(UART mode) [CX3061]  
R5F21272NFP@QFP32 [CX3061]  
R5F21272NFP@QFP32(single ISP) [CX0001]  
R5F21272NFP@QFP32(single wire) [CX3061]  
R5F21272NFP@QFP32(UART ISP) [CX0001]  
R5F21272NFP@QFP32(UART mode) [CX3061]  
R5F21272SDFP@QFP32 [CX3061]  
R5F21272SDFP@QFP32(single ISP) [CX0001]  
R5F21272SDFP@QFP32(single wire) [CX3061]  
R5F21272SDFP@QFP32(UART ISP) [CX0001]  
R5F21272SDFP@QFP32(UART mode) [CX3061]  
R5F21272SJFP@QFP32 [CX3061]  
R5F21272SJFP@QFP32(single ISP) [CX0001]  
R5F21272SJFP@QFP32(single wire) [CX3061]  
R5F21272SJFP@QFP32(UART ISP) [CX0001]  
R5F21272SJFP@QFP32(UART mode) [CX3061]  
R5F21272SKFP@QFP32 [CX3061]  
R5F21272SKFP@QFP32(single ISP) [CX0001]  
R5F21272SKFP@QFP32(single wire) [CX3061]  
R5F21272SKFP@QFP32(UART ISP) [CX0001]  
R5F21272SKFP@QFP32(UART mode) [CX3061]  
R5F21272SNFP@QFP32 [CX3061]  
R5F21272SNFP@QFP32(single ISP) [CX0001]  
R5F21272SNFP@QFP32(single wire) [CX3061]  
R5F21272SNFP@QFP32(UART ISP) [CX0001]  
R5F21272SNFP@QFP32(UART mode) [CX3061]  
R5F21274DFP@QFP32 [CX3061]  
R5F21274DFP@QFP32(single ISP) [CX0001]  
R5F21274DFP@QFP32(single wire) [CX3061]  
R5F21274DFP@QFP32(UART ISP) [CX0001]  
R5F21274DFP@QFP32(UART mode) [CX3061]  
R5F21274JFP@QFP32 [CX3061]

R5F21274JFP@QFP32(single ISP) [CX0001]  
R5F21274JFP@QFP32(single wire) [CX3061]  
R5F21274JFP@QFP32(UART ISP) [CX0001]  
R5F21274JFP@QFP32(UART mode) [CX3061]  
R5F21274KFP@QFP32 [CX3061]  
R5F21274KFP@QFP32(single ISP) [CX0001]  
R5F21274KFP@QFP32(single wire) [CX3061]  
R5F21274KFP@QFP32(UART ISP) [CX0001]  
R5F21274KFP@QFP32(UART mode) [CX3061]  
R5F21274NFP@QFP32 [CX3061]  
R5F21274NFP@QFP32(single ISP) [CX0001]  
R5F21274NFP@QFP32(single wire) [CX3061]  
R5F21274NFP@QFP32(UART ISP) [CX0001]  
R5F21274NFP@QFP32(UART mode) [CX3061]  
R5F21274SDFP@QFP32 [CX3061]  
R5F21274SDFP@QFP32(single ISP) [CX0001]  
R5F21274SDFP@QFP32(single wire) [CX3061]  
R5F21274SDFP@QFP32(UART ISP) [CX0001]  
R5F21274SDFP@QFP32(UART mode) [CX3061]  
R5F21274SJFP@QFP32 [CX3061]  
R5F21274SJFP@QFP32(single ISP) [CX0001]  
R5F21274SJFP@QFP32(single wire) [CX3061]  
R5F21274SJFP@QFP32(UART ISP) [CX0001]  
R5F21274SJFP@QFP32(UART mode) [CX3061]  
R5F21274SKFP@QFP32 [CX3061]  
R5F21274SKFP@QFP32(single ISP) [CX0001]  
R5F21274SKFP@QFP32(single wire) [CX3061]  
R5F21274SKFP@QFP32(UART ISP) [CX0001]  
R5F21274SKFP@QFP32(UART mode) [CX3061]  
R5F21274SNFP@QFP32 [CX3061]  
R5F21274SNFP@QFP32(single ISP) [CX0001]  
R5F21274SNFP@QFP32(single wire) [CX3061]  
R5F21274SNFP@QFP32(UART ISP) [CX0001]  
R5F21274SNFP@QFP32(UART mode) [CX3061]  
R5F21275DFP@QFP32 [CX3061]  
R5F21275DFP@QFP32(single ISP) [CX0001]  
R5F21275DFP@QFP32(single wire) [CX3061]  
R5F21275DFP@QFP32(UART ISP) [CX0001]  
R5F21275DFP@QFP32(UART mode) [CX3061]  
R5F21275JFP@QFP32 [CX3061]  
R5F21275JFP@QFP32(single ISP) [CX0001]  
R5F21275JFP@QFP32(single wire) [CX3061]  
R5F21275JFP@QFP32(UART ISP) [CX0001]  
R5F21275JFP@QFP32(UART mode) [CX3061]  
R5F21275KFP@QFP32 [CX3061]  
R5F21275KFP@QFP32(single ISP) [CX0001]  
R5F21275KFP@QFP32(single wire) [CX3061]  
R5F21275KFP@QFP32(UART ISP) [CX0001]  
R5F21275KFP@QFP32(UART mode) [CX3061]  
R5F21275NFP@QFP32 [CX3061]  
R5F21275NFP@QFP32(single ISP) [CX0001]  
R5F21275NFP@QFP32(single wire) [CX3061]  
R5F21275NFP@QFP32(UART ISP) [CX0001]  
R5F21275NFP@QFP32(UART mode) [CX3061]  
R5F21275SDFP@QFP32 [CX3061]  
R5F21275SDFP@QFP32(single ISP) [CX0001]  
R5F21275SDFP@QFP32(single wire) [CX3061]  
R5F21275SDFP@QFP32(UART ISP) [CX0001]  
R5F21275SDFP@QFP32(UART mode) [CX3061]

R5F21275SJFP@QFP32 [CX3061]  
R5F21275SJFP@QFP32(single ISP) [CX0001]  
R5F21275SJFP@QFP32(single wire) [CX3061]  
R5F21275SJFP@QFP32(UART ISP) [CX0001]  
R5F21275SJFP@QFP32(UART mode) [CX3061]  
R5F21275SKFP@QFP32 [CX3061]  
R5F21275SKFP@QFP32(single ISP) [CX0001]  
R5F21275SKFP@QFP32(single wire) [CX3061]  
R5F21275SKFP@QFP32(UART ISP) [CX0001]  
R5F21275SKFP@QFP32(UART mode) [CX3061]  
R5F21275SNFP@QFP32 [CX3061]  
R5F21275SNFP@QFP32(single ISP) [CX0001]  
R5F21275SNFP@QFP32(single wire) [CX3061]  
R5F21275SNFP@QFP32(UART ISP) [CX0001]  
R5F21275SNFP@QFP32(UART mode) [CX3061]  
R5F21276DFP@QFP32 [CX3061]  
R5F21276DFP@QFP32(single ISP) [CX0001]  
R5F21276DFP@QFP32(single wire) [CX3061]  
R5F21276DFP@QFP32(UART ISP) [CX0001]  
R5F21276DFP@QFP32(UART mode) [CX3061]  
R5F21276JFP@QFP32 [CX3061]  
R5F21276JFP@QFP32(single ISP) [CX0001]  
R5F21276JFP@QFP32(single wire) [CX3061]  
R5F21276JFP@QFP32(UART ISP) [CX0001]  
R5F21276JFP@QFP32(UART mode) [CX3061]  
R5F21276KFP@QFP32 [CX3061]  
R5F21276KFP@QFP32(single ISP) [CX0001]  
R5F21276KFP@QFP32(single wire) [CX3061]  
R5F21276KFP@QFP32(UART ISP) [CX0001]  
R5F21276KFP@QFP32(UART mode) [CX3061]  
R5F21276NFP@QFP32 [CX3061]  
R5F21276NFP@QFP32(single ISP) [CX0001]  
R5F21276NFP@QFP32(single wire) [CX3061]  
R5F21276NFP@QFP32(UART ISP) [CX0001]  
R5F21276NFP@QFP32(UART mode) [CX3061]  
R5F21276SDFP@QFP32 [CX3061]  
R5F21276SDFP@QFP32(single ISP) [CX0001]  
R5F21276SDFP@QFP32(single wire) [CX3061]  
R5F21276SDFP@QFP32(UART ISP) [CX0001]  
R5F21276SDFP@QFP32(UART mode) [CX3061]  
R5F21276SJFP@QFP32 [CX3061]  
R5F21276SJFP@QFP32(single ISP) [CX0001]  
R5F21276SJFP@QFP32(single wire) [CX3061]  
R5F21276SJFP@QFP32(UART ISP) [CX0001]  
R5F21276SJFP@QFP32(UART mode) [CX3061]  
R5F21276SKFP@QFP32 [CX3061]  
R5F21276SKFP@QFP32(single ISP) [CX0001]  
R5F21276SKFP@QFP32(single wire) [CX3061]  
R5F21276SKFP@QFP32(UART ISP) [CX0001]  
R5F21276SKFP@QFP32(UART mode) [CX3061]  
R5F21276SNFP@QFP32 [CX3061]  
R5F21276SNFP@QFP32(single ISP) [CX0001]  
R5F21276SNFP@QFP32(single wire) [CX3061]  
R5F21276SNFP@QFP32(UART ISP) [CX0001]  
R5F21276SNFP@QFP32(UART mode) [CX3061]  
R5F21282DSP@SOIC20 [CX1000]  
R5F21282DSP@SOIC20(single ISP) [CX0001]  
R5F21282DSP@SOIC20(single wire) [CX1000]  
R5F21282DSP@SOIC20(UART ISP) [CX0001]

R5F21282DSP@SOIC20(UART mode) [CX1000]  
R5F21282JSP@SOIC20 [CX1000]  
R5F21282JSP@SOIC20(single ISP) [CX0001]  
R5F21282JSP@SOIC20(single wire) [CX1000]  
R5F21282JSP@SOIC20(UART ISP) [CX0001]  
R5F21282JSP@SOIC20(UART mode) [CX1000]  
R5F21282KSP@SOIC20 [CX1000]  
R5F21282KSP@SOIC20(single ISP) [CX0001]  
R5F21282KSP@SOIC20(single wire) [CX1000]  
R5F21282KSP@SOIC20(UART ISP) [CX0001]  
R5F21282KSP@SOIC20(UART mode) [CX1000]  
R5F21282NSP@SOIC20 [CX1000]  
R5F21282NSP@SOIC20(single ISP) [CX0001]  
R5F21282NSP@SOIC20(single wire) [CX1000]  
R5F21282NSP@SOIC20(UART ISP) [CX0001]  
R5F21282NSP@SOIC20(UART mode) [CX1000]  
R5F21282SDSP@SOIC20 [CX1000]  
R5F21282SDSP@SOIC20(single ISP) [CX0001]  
R5F21282SDSP@SOIC20(single wire) [CX1000]  
R5F21282SDSP@SOIC20(UART ISP) [CX0001]  
R5F21282SDSP@SOIC20(UART mode) [CX1000]  
R5F21282SJSP@SOIC20 [CX1000]  
R5F21282SJSP@SOIC20(single ISP) [CX0001]  
R5F21282SJSP@SOIC20(single wire) [CX1000]  
R5F21282SJSP@SOIC20(UART ISP) [CX0001]  
R5F21282SJSP@SOIC20(UART mode) [CX1000]  
R5F21282SKSP@SOIC20 [CX1000]  
R5F21282SKSP@SOIC20(single ISP) [CX0001]  
R5F21282SKSP@SOIC20(single wire) [CX1000]  
R5F21282SKSP@SOIC20(UART ISP) [CX0001]  
R5F21282SKSP@SOIC20(UART mode) [CX1000]  
R5F21282SNSP@SOIC20 [CX1000]  
R5F21282SNSP@SOIC20(single ISP) [CX0001]  
R5F21282SNSP@SOIC20(single wire) [CX1000]  
R5F21282SNSP@SOIC20(UART ISP) [CX0001]  
R5F21282SNSP@SOIC20(UART mode) [CX1000]  
R5F21284DSP@SOIC20 [CX1000]  
R5F21284DSP@SOIC20(single ISP) [CX0001]  
R5F21284DSP@SOIC20(single wire) [CX1000]  
R5F21284DSP@SOIC20(UART ISP) [CX0001]  
R5F21284DSP@SOIC20(UART mode) [CX1000]  
R5F21284JSP@SOIC20 [CX1000]  
R5F21284JSP@SOIC20(single ISP) [CX0001]  
R5F21284JSP@SOIC20(single wire) [CX1000]  
R5F21284JSP@SOIC20(UART ISP) [CX0001]  
R5F21284JSP@SOIC20(UART mode) [CX1000]  
R5F21284KSP@SOIC20 [CX1000]  
R5F21284KSP@SOIC20(single ISP) [CX0001]  
R5F21284KSP@SOIC20(single wire) [CX1000]  
R5F21284KSP@SOIC20(UART ISP) [CX0001]  
R5F21284KSP@SOIC20(UART mode) [CX1000]  
R5F21284NSP@SOIC20 [CX1000]  
R5F21284NSP@SOIC20(single ISP) [CX0001]  
R5F21284NSP@SOIC20(single wire) [CX1000]  
R5F21284NSP@SOIC20(UART ISP) [CX0001]  
R5F21284NSP@SOIC20(UART mode) [CX1000]  
R5F21284SDSP@SOIC20 [CX1000]  
R5F21284SDSP@SOIC20(single ISP) [CX0001]  
R5F21284SDSP@SOIC20(single wire) [CX1000]

R5F21284SDSP@SOIC20(UART ISP) [CX0001]  
R5F21284SDSP@SOIC20(UART mode) [CX1000]  
R5F21284SJSP@SOIC20 [CX1000]  
R5F21284SJSP@SOIC20(single ISP) [CX0001]  
R5F21284SJSP@SOIC20(single wire) [CX1000]  
R5F21284SJSP@SOIC20(UART ISP) [CX0001]  
R5F21284SJSP@SOIC20(UART mode) [CX1000]  
R5F21284SKSP@SOIC20 [CX1000]  
R5F21284SKSP@SOIC20(single ISP) [CX0001]  
R5F21284SKSP@SOIC20(single wire) [CX1000]  
R5F21284SKSP@SOIC20(UART ISP) [CX0001]  
R5F21284SKSP@SOIC20(UART mode) [CX1000]  
R5F21284SNSP@SOIC20 [CX1000]  
R5F21284SNSP@SOIC20(single ISP) [CX0001]  
R5F21284SNSP@SOIC20(single wire) [CX1000]  
R5F21284SNSP@SOIC20(UART ISP) [CX0001]  
R5F21284SNSP@SOIC20(UART mode) [CX1000]  
R5F21292DSP@SOIC20 [CX1000]  
R5F21292DSP@SOIC20(single ISP) [CX0001]  
R5F21292DSP@SOIC20(single wire) [CX1000]  
R5F21292DSP@SOIC20(UART ISP) [CX0001]  
R5F21292DSP@SOIC20(UART mode) [CX1000]  
R5F21292JSP@SOIC20 [CX1000]  
R5F21292JSP@SOIC20(single ISP) [CX0001]  
R5F21292JSP@SOIC20(single wire) [CX1000]  
R5F21292JSP@SOIC20(UART ISP) [CX0001]  
R5F21292JSP@SOIC20(UART mode) [CX1000]  
R5F21292KSP@SOIC20 [CX1000]  
R5F21292KSP@SOIC20(single ISP) [CX0001]  
R5F21292KSP@SOIC20(single wire) [CX1000]  
R5F21292KSP@SOIC20(UART ISP) [CX0001]  
R5F21292KSP@SOIC20(UART mode) [CX1000]  
R5F21292NSP@SOIC20 [CX1000]  
R5F21292NSP@SOIC20(single ISP) [CX0001]  
R5F21292NSP@SOIC20(single wire) [CX1000]  
R5F21292NSP@SOIC20(UART ISP) [CX0001]  
R5F21292NSP@SOIC20(UART mode) [CX1000]  
R5F21292SDSP@SOIC20 [CX1000]  
R5F21292SDSP@SOIC20(single ISP) [CX0001]  
R5F21292SDSP@SOIC20(single wire) [CX1000]  
R5F21292SDSP@SOIC20(UART ISP) [CX0001]  
R5F21292SDSP@SOIC20(UART mode) [CX1000]  
R5F21292SJSP@SOIC20 [CX1000]  
R5F21292SJSP@SOIC20(single ISP) [CX0001]  
R5F21292SJSP@SOIC20(single wire) [CX1000]  
R5F21292SJSP@SOIC20(UART ISP) [CX0001]  
R5F21292SJSP@SOIC20(UART mode) [CX1000]  
R5F21292SKSP@SOIC20 [CX1000]  
R5F21292SKSP@SOIC20(single ISP) [CX0001]  
R5F21292SKSP@SOIC20(single wire) [CX1000]  
R5F21292SKSP@SOIC20(UART ISP) [CX0001]  
R5F21292SKSP@SOIC20(UART mode) [CX1000]  
R5F21292SNSP@SOIC20 [CX1000]  
R5F21292SNSP@SOIC20(single ISP) [CX0001]  
R5F21292SNSP@SOIC20(single wire) [CX1000]  
R5F21292SNSP@SOIC20(UART ISP) [CX0001]  
R5F21292SNSP@SOIC20(UART mode) [CX1000]  
R5F21294DSP@SOIC20 [CX1000]  
R5F21294DSP@SOIC20(single ISP) [CX0001]

R5F21294DSP@SOIC20(single wire) [CX1000]  
R5F21294DSP@SOIC20(UART ISP) [CX0001]  
R5F21294DSP@SOIC20(UART mode) [CX1000]  
R5F21294JSP@SOIC20 [CX1000]  
R5F21294JSP@SOIC20(single ISP) [CX0001]  
R5F21294JSP@SOIC20(single wire) [CX1000]  
R5F21294JSP@SOIC20(UART ISP) [CX0001]  
R5F21294JSP@SOIC20(UART mode) [CX1000]  
R5F21294KSP@SOIC20 [CX1000]  
R5F21294KSP@SOIC20(single ISP) [CX0001]  
R5F21294KSP@SOIC20(single wire) [CX1000]  
R5F21294KSP@SOIC20(UART ISP) [CX0001]  
R5F21294KSP@SOIC20(UART mode) [CX1000]  
R5F21294NSP@SOIC20 [CX1000]  
R5F21294NSP@SOIC20(single ISP) [CX0001]  
R5F21294NSP@SOIC20(single wire) [CX1000]  
R5F21294NSP@SOIC20(UART ISP) [CX0001]  
R5F21294NSP@SOIC20(UART mode) [CX1000]  
R5F21294SDSP@SOIC20 [CX1000]  
R5F21294SDSP@SOIC20(single ISP) [CX0001]  
R5F21294SDSP@SOIC20(single wire) [CX1000]  
R5F21294SDSP@SOIC20(UART ISP) [CX0001]  
R5F21294SDSP@SOIC20(UART mode) [CX1000]  
R5F21294SJSP@SOIC20 [CX1000]  
R5F21294SJSP@SOIC20(single ISP) [CX0001]  
R5F21294SJSP@SOIC20(single wire) [CX1000]  
R5F21294SJSP@SOIC20(UART ISP) [CX0001]  
R5F21294SJSP@SOIC20(UART mode) [CX1000]  
R5F21294SKSP@SOIC20 [CX1000]  
R5F21294SKSP@SOIC20(single ISP) [CX0001]  
R5F21294SKSP@SOIC20(single wire) [CX1000]  
R5F21294SKSP@SOIC20(UART ISP) [CX0001]  
R5F21294SKSP@SOIC20(UART mode) [CX1000]  
R5F21294SNSP@SOIC20 [CX1000]  
R5F21294SNSP@SOIC20(single ISP) [CX0001]  
R5F21294SNSP@SOIC20(single wire) [CX1000]  
R5F21294SNSP@SOIC20(UART ISP) [CX0001]  
R5F21294SNSP@SOIC20(UART mode) [CX1000]  
R5F212A7SDFA@TQFP64 [CX3044]  
R5F212A7SDFA@TQFP64(single ISP) [CX0001]  
R5F212A7SDFA@TQFP64(single wire) [CX3013]  
R5F212A7SDFA@TQFP64(UART ISP) [CX0001]  
R5F212A7SDFA@TQFP64(UART mode) [CX3013]  
R5F212A7SDFP@TQFP64 [CX3011]  
R5F212A7SDFP@TQFP64(single ISP) [CX0001]  
R5F212A7SDFP@TQFP64(single wire) [CX3011]  
R5F212A7SDFP@TQFP64(UART ISP) [CX0001]  
R5F212A7SDFP@TQFP64(UART mode) [CX3011]  
R5F212A7SNFA@TQFP64 [CX3044]  
R5F212A7SNFA@TQFP64(single ISP) [CX0001]  
R5F212A7SNFA@TQFP64(single wire) [CX3013]  
R5F212A7SNFA@TQFP64(UART ISP) [CX0001]  
R5F212A7SNFA@TQFP64(UART mode) [CX3013]  
R5F212A7SNFP@TQFP64 [CX3011]  
R5F212A7SNFP@TQFP64(single ISP) [CX0001]  
R5F212A7SNFP@TQFP64(single wire) [CX3011]  
R5F212A7SNFP@TQFP64(UART ISP) [CX0001]  
R5F212A7SNFP@TQFP64(UART mode) [CX3011]  
R5F212A8SDFA@TQFP64 [CX3044]

R5F212A8SDFA@TQFP64(single ISP) [CX0001]  
R5F212A8SDFA@TQFP64(single wire) [CX3013]  
R5F212A8SDFA@TQFP64(UART ISP) [CX0001]  
R5F212A8SDFA@TQFP64(UART mode) [CX3013]  
R5F212A8SDFP@TQFP64 [CX3011]  
R5F212A8SDFP@TQFP64(single ISP) [CX0001]  
R5F212A8SDFP@TQFP64(single wire) [CX3011]  
R5F212A8SDFP@TQFP64(UART ISP) [CX0001]  
R5F212A8SDFP@TQFP64(UART mode) [CX3011]  
R5F212A8SNFA@TQFP64 [CX3044]  
R5F212A8SNFA@TQFP64(single ISP) [CX0001]  
R5F212A8SNFA@TQFP64(single wire) [CX3013]  
R5F212A8SNFA@TQFP64(UART ISP) [CX0001]  
R5F212A8SNFA@TQFP64(UART mode) [CX3013]  
R5F212A8SNFP@TQFP64 [CX3011]  
R5F212A8SNFP@TQFP64(single ISP) [CX0001]  
R5F212A8SNFP@TQFP64(single wire) [CX3011]  
R5F212A8SNFP@TQFP64(UART ISP) [CX0001]  
R5F212A8SNFP@TQFP64(UART mode) [CX3011]  
R5F212AASDFA@TQFP64 [CX3044]  
R5F212AASDFA@TQFP64(single ISP) [CX0001]  
R5F212AASDFA@TQFP64(single wire) [CX3013]  
R5F212AASDFA@TQFP64(UART ISP) [CX0001]  
R5F212AASDFA@TQFP64(UART mode) [CX3013]  
R5F212AASDFP@TQFP64 [CX3011]  
R5F212AASDFP@TQFP64(single ISP) [CX0001]  
R5F212AASDFP@TQFP64(single wire) [CX3011]  
R5F212AASDFP@TQFP64(UART ISP) [CX0001]  
R5F212AASDFP@TQFP64(UART mode) [CX3011]  
R5F212AASNFA@TQFP64 [CX3044]  
R5F212AASNFA@TQFP64(single ISP) [CX0001]  
R5F212AASNFA@TQFP64(single wire) [CX3013]  
R5F212AASNFA@TQFP64(UART ISP) [CX0001]  
R5F212AASNFA@TQFP64(UART mode) [CX3013]  
R5F212AASNFP@TQFP64 [CX3011]  
R5F212AASNFP@TQFP64(single ISP) [CX0001]  
R5F212AASNFP@TQFP64(single wire) [CX3011]  
R5F212AASNFP@TQFP64(UART ISP) [CX0001]  
R5F212AASNFP@TQFP64(UART mode) [CX3011]  
R5F212ACSDFA@TQFP64 [CX3044]  
R5F212ACSDFA@TQFP64(single ISP) [CX0001]  
R5F212ACSDFA@TQFP64(single wire) [CX3013]  
R5F212ACSDFA@TQFP64(UART ISP) [CX0001]  
R5F212ACSDFA@TQFP64(UART mode) [CX3013]  
R5F212ACSDFP@TQFP64 [CX3011]  
R5F212ACSDFP@TQFP64(single ISP) [CX0001]  
R5F212ACSDFP@TQFP64(single wire) [CX3011]  
R5F212ACSDFP@TQFP64(UART ISP) [CX0001]  
R5F212ACSDFP@TQFP64(UART mode) [CX3011]  
R5F212ACSNFA@TQFP64 [CX3044]  
R5F212ACSNFA@TQFP64(single ISP) [CX0001]  
R5F212ACSNFA@TQFP64(single wire) [CX3013]  
R5F212ACSNFA@TQFP64(UART ISP) [CX0001]  
R5F212ACSNFA@TQFP64(UART mode) [CX3013]  
R5F212ACSNFP@TQFP64 [CX3011]  
R5F212ACSNFP@TQFP64(single ISP) [CX0001]  
R5F212ACSNFP@TQFP64(single wire) [CX3011]  
R5F212ACSNFP@TQFP64(UART ISP) [CX0001]  
R5F212ACSNFP@TQFP64(UART mode) [CX3011]



R5F212B7SDFA@TQFP64 [CX3044]  
R5F212B7SDFA@TQFP64(single ISP) [CX0001]  
R5F212B7SDFA@TQFP64(single wire) [CX3013]  
R5F212B7SDFA@TQFP64(UART ISP) [CX0001]  
R5F212B7SDFA@TQFP64(UART mode) [CX3013]  
R5F212B7SDFP@TQFP64 [CX3011]  
R5F212B7SDFP@TQFP64(single ISP) [CX0001]  
R5F212B7SDFP@TQFP64(single wire) [CX3011]  
R5F212B7SDFP@TQFP64(UART ISP) [CX0001]  
R5F212B7SDFP@TQFP64(UART mode) [CX3011]  
R5F212B7SNFA@TQFP64 [CX3044]  
R5F212B7SNFA@TQFP64(single ISP) [CX0001]  
R5F212B7SNFA@TQFP64(single wire) [CX3013]  
R5F212B7SNFA@TQFP64(UART ISP) [CX0001]  
R5F212B7SNFA@TQFP64(UART mode) [CX3013]  
R5F212B7SNFP@TQFP64 [CX3011]  
R5F212B7SNFP@TQFP64(single ISP) [CX0001]  
R5F212B7SNFP@TQFP64(single wire) [CX3011]  
R5F212B7SNFP@TQFP64(UART ISP) [CX0001]  
R5F212B7SNFP@TQFP64(UART mode) [CX3011]  
R5F212B8SDFA@TQFP64 [CX3044]  
R5F212B8SDFA@TQFP64(single ISP) [CX0001]  
R5F212B8SDFA@TQFP64(single wire) [CX3013]  
R5F212B8SDFA@TQFP64(UART ISP) [CX0001]  
R5F212B8SDFA@TQFP64(UART mode) [CX3013]  
R5F212B8SDFP@TQFP64 [CX3011]  
R5F212B8SDFP@TQFP64(single ISP) [CX0001]  
R5F212B8SDFP@TQFP64(single wire) [CX3011]  
R5F212B8SDFP@TQFP64(UART ISP) [CX0001]  
R5F212B8SDFP@TQFP64(UART mode) [CX3011]  
R5F212B8SNFA@TQFP64 [CX3044]  
R5F212B8SNFA@TQFP64(single ISP) [CX0001]  
R5F212B8SNFA@TQFP64(single wire) [CX3013]  
R5F212B8SNFA@TQFP64(UART ISP) [CX0001]  
R5F212B8SNFA@TQFP64(UART mode) [CX3013]  
R5F212B8SNFP@TQFP64 [CX3011]  
R5F212B8SNFP@TQFP64(single ISP) [CX0001]  
R5F212B8SNFP@TQFP64(single wire) [CX3011]  
R5F212B8SNFP@TQFP64(UART ISP) [CX0001]  
R5F212B8SNFP@TQFP64(UART mode) [CX3011]  
R5F212BASDFA@TQFP64 [CX3044]  
R5F212BASDFA@TQFP64(single ISP) [CX0001]  
R5F212BASDFA@TQFP64(single wire) [CX3013]  
R5F212BASDFA@TQFP64(UART ISP) [CX0001]  
R5F212BASDFA@TQFP64(UART mode) [CX3013]  
R5F212BASDFP@TQFP64 [CX3011]  
R5F212BASDFP@TQFP64(single ISP) [CX0001]  
R5F212BASDFP@TQFP64(single wire) [CX3011]  
R5F212BASDFP@TQFP64(UART ISP) [CX0001]  
R5F212BASDFP@TQFP64(UART mode) [CX3011]  
R5F212BASNFA@TQFP64 [CX3044]  
R5F212BASNFA@TQFP64(single ISP) [CX0001]  
R5F212BASNFA@TQFP64(single wire) [CX3013]  
R5F212BASNFA@TQFP64(UART ISP) [CX0001]  
R5F212BASNFA@TQFP64(UART mode) [CX3013]  
R5F212BASNFP@TQFP64 [CX3011]  
R5F212BASNFP@TQFP64(single ISP) [CX0001]  
R5F212BASNFP@TQFP64(single wire) [CX3011]  
R5F212BASNFP@TQFP64(UART ISP) [CX0001]

R5F212BASNFP@TQFP64(UART mode) [CX3011]  
R5F212BCSDFA@TQFP64 [CX3044]  
R5F212BCSDFA@TQFP64(single ISP) [CX0001]  
R5F212BCSDFA@TQFP64(single wire) [CX3013]  
R5F212BCSDFA@TQFP64(UART ISP) [CX0001]  
R5F212BCSDFA@TQFP64(UART mode) [CX3013]  
R5F212BCSDFP@TQFP64 [CX3011]  
R5F212BCSDFP@TQFP64(single ISP) [CX0001]  
R5F212BCSDFP@TQFP64(single wire) [CX3011]  
R5F212BCSDFP@TQFP64(UART ISP) [CX0001]  
R5F212BCSDFP@TQFP64(UART mode) [CX3011]  
R5F212BCSNFA@TQFP64 [CX3044]  
R5F212BCSNFA@TQFP64(single ISP) [CX0001]  
R5F212BCSNFA@TQFP64(single wire) [CX3013]  
R5F212BCSNFA@TQFP64(UART ISP) [CX0001]  
R5F212BCSNFA@TQFP64(UART mode) [CX3013]  
R5F212BCSNFP@TQFP64 [CX3011]  
R5F212BCSNFP@TQFP64(single ISP) [CX0001]  
R5F212BCSNFP@TQFP64(single wire) [CX3011]  
R5F212BCSNFP@TQFP64(UART ISP) [CX0001]  
R5F212BCSNFP@TQFP64(UART mode) [CX3011]  
R5F212C7SDFP@TQFP80 [CX3016]  
R5F212C7SDFP@TQFP80(single ISP) [CX0001]  
R5F212C7SDFP@TQFP80(single wire) [CX3016]  
R5F212C7SDFP@TQFP80(UART ISP) [CX0001]  
R5F212C7SDFP@TQFP80(UART mode) [CX3016]  
R5F212C7SNFP@TQFP80 [CX3016]  
R5F212C7SNFP@TQFP80(single ISP) [CX0001]  
R5F212C7SNFP@TQFP80(single wire) [CX3016]  
R5F212C7SNFP@TQFP80(UART ISP) [CX0001]  
R5F212C7SNFP@TQFP80(UART mode) [CX3016]  
R5F212C8SDFP@TQFP80 [CX3016]  
R5F212C8SDFP@TQFP80(single ISP) [CX0001]  
R5F212C8SDFP@TQFP80(single wire) [CX3016]  
R5F212C8SDFP@TQFP80(UART ISP) [CX0001]  
R5F212C8SDFP@TQFP80(UART mode) [CX3016]  
R5F212C8SNFP@TQFP80 [CX3016]  
R5F212C8SNFP@TQFP80(single ISP) [CX0001]  
R5F212C8SNFP@TQFP80(single wire) [CX3016]  
R5F212C8SNFP@TQFP80(UART ISP) [CX0001]  
R5F212C8SNFP@TQFP80(UART mode) [CX3016]  
R5F212CASDFP@TQFP80 [CX3016]  
R5F212CASDFP@TQFP80(single ISP) [CX0001]  
R5F212CASDFP@TQFP80(single wire) [CX3016]  
R5F212CASDFP@TQFP80(UART ISP) [CX0001]  
R5F212CASDFP@TQFP80(UART mode) [CX3016]  
R5F212CASNFP@TQFP80 [CX3016]  
R5F212CASNFP@TQFP80(single ISP) [CX0001]  
R5F212CASNFP@TQFP80(single wire) [CX3016]  
R5F212CASNFP@TQFP80(UART ISP) [CX0001]  
R5F212CASNFP@TQFP80(UART mode) [CX3016]  
R5F212CCSDFP@TQFP80 [CX3016]  
R5F212CCSDFP@TQFP80(single ISP) [CX0001]  
R5F212CCSDFP@TQFP80(single wire) [CX3016]  
R5F212CCSDFP@TQFP80(UART ISP) [CX0001]  
R5F212CCSDFP@TQFP80(UART mode) [CX3016]  
R5F212CCSNFP@TQFP80 [CX3016]  
R5F212CCSNFP@TQFP80(single ISP) [CX0001]  
R5F212CCSNFP@TQFP80(single wire) [CX3016]

R5F212CCSNFP@TQFP80(UART ISP) [CX0001]  
R5F212CCSNFP@TQFP80(UART mode) [CX3016]  
R5F212D7SDFP@TQFP80 [CX3016]  
R5F212D7SDFP@TQFP80(single ISP) [CX0001]  
R5F212D7SDFP@TQFP80(single wire) [CX3016]  
R5F212D7SDFP@TQFP80(UART ISP) [CX0001]  
R5F212D7SDFP@TQFP80(UART mode) [CX3016]  
R5F212D7SNFP@TQFP80 [CX3016]  
R5F212D7SNFP@TQFP80(single ISP) [CX0001]  
R5F212D7SNFP@TQFP80(single wire) [CX3016]  
R5F212D7SNFP@TQFP80(UART ISP) [CX0001]  
R5F212D7SNFP@TQFP80(UART mode) [CX3016]  
R5F212D8SDFP@TQFP80 [CX3016]  
R5F212D8SDFP@TQFP80(single ISP) [CX0001]  
R5F212D8SDFP@TQFP80(single wire) [CX3016]  
R5F212D8SDFP@TQFP80(UART ISP) [CX0001]  
R5F212D8SDFP@TQFP80(UART mode) [CX3016]  
R5F212D8SNFP@TQFP80 [CX3016]  
R5F212D8SNFP@TQFP80(single ISP) [CX0001]  
R5F212D8SNFP@TQFP80(single wire) [CX3016]  
R5F212D8SNFP@TQFP80(UART ISP) [CX0001]  
R5F212D8SNFP@TQFP80(UART mode) [CX3016]  
R5F212DASDFP@TQFP80 [CX3016]  
R5F212DASDFP@TQFP80(single ISP) [CX0001]  
R5F212DASDFP@TQFP80(single wire) [CX3016]  
R5F212DASDFP@TQFP80(UART ISP) [CX0001]  
R5F212DASDFP@TQFP80(UART mode) [CX3016]  
R5F212DASNFP@TQFP80 [CX3016]  
R5F212DASNFP@TQFP80(single ISP) [CX0001]  
R5F212DASNFP@TQFP80(single wire) [CX3016]  
R5F212DASNFP@TQFP80(UART ISP) [CX0001]  
R5F212DASNFP@TQFP80(UART mode) [CX3016]  
R5F212DCSDFP@TQFP80 [CX3016]  
R5F212DCSDFP@TQFP80(single ISP) [CX0001]  
R5F212DCSDFP@TQFP80(single wire) [CX3016]  
R5F212DCSDFP@TQFP80(UART ISP) [CX0001]  
R5F212DCSDFP@TQFP80(UART mode) [CX3016]  
R5F212DCSNFP@TQFP80 [CX3016]  
R5F212DCSNFP@TQFP80(single ISP) [CX0001]  
R5F212DCSNFP@TQFP80(single wire) [CX3016]  
R5F212DCSNFP@TQFP80(UART ISP) [CX0001]  
R5F212DCSNFP@TQFP80(UART mode) [CX3016]  
R5F212G4SDFP@QFP32 [CX3061]  
R5F212G4SDFP@QFP32(single ISP) [CX0001]  
R5F212G4SDFP@QFP32(single wire) [CX3061]  
R5F212G4SNFP@QFP32 [CX3061]  
R5F212G4SNFP@QFP32(single ISP) [CX0001]  
R5F212G4SNFP@QFP32(single wire) [CX3061]  
R5F212G5SDFP@QFP32 [CX3061]  
R5F212G5SDFP@QFP32(single ISP) [CX0001]  
R5F212G5SDFP@QFP32(single wire) [CX3061]  
R5F212G5SNFP@QFP32 [CX3061]  
R5F212G5SNFP@QFP32(single ISP) [CX0001]  
R5F212G5SNFP@QFP32(single wire) [CX3061]  
R5F212G6SDFP@QFP32 [CX3061]  
R5F212G6SDFP@QFP32(single ISP) [CX0001]  
R5F212G6SDFP@QFP32(single wire) [CX3061]  
R5F212G6SNFP@QFP32 [CX3061]  
R5F212G6SNFP@QFP32(single ISP) [CX0001]

R5F212G6SNFP@QFP32(single wire) [CX3061]  
R5F212H1SDSP@TSSOP20 [CX1000]  
R5F212H1SDSP@TSSOP20(single ISP) [CX0001]  
R5F212H1SDSP@TSSOP20(single) [CX1000]  
R5F212H1SNSP@TSSOP20 [CX1000]  
R5F212H1SNSP@TSSOP20(single ISP) [CX0001]  
R5F212H1SNSP@TSSOP20(single) [CX1000]  
R5F212H2SDSP@TSSOP20 [CX1000]  
R5F212H2SDSP@TSSOP20(single ISP) [CX0001]  
R5F212H2SDSP@TSSOP20(single) [CX1000]  
R5F212H2SNSP@TSSOP20 [CX1000]  
R5F212H2SNSP@TSSOP20(single ISP) [CX0001]  
R5F212H2SNSP@TSSOP20(single) [CX1000]  
R5F212J0SDSP@TSSOP20 [CX1000]  
R5F212J0SDSP@TSSOP20(single ISP) [CX0001]  
R5F212J0SDSP@TSSOP20(single) [CX1000]  
R5F212J0SNSP@TSSOP20 [CX1000]  
R5F212J0SNSP@TSSOP20(single ISP) [CX0001]  
R5F212J0SNSP@TSSOP20(single) [CX1000]  
R5F212J1SDSP@TSSOP20 [CX1000]  
R5F212J1SDSP@TSSOP20(single ISP) [CX0001]  
R5F212J1SDSP@TSSOP20(single) [CX1000]  
R5F212J1SNSP@TSSOP20 [CX1000]  
R5F212J1SNSP@TSSOP20(single ISP) [CX0001]  
R5F212J1SNSP@TSSOP20(single) [CX1000]  
R5F212K2SDFP@QFP32 [CX3061]  
R5F212K2SDFP@QFP32(single ISP) [CX0001]  
R5F212K2SDFP@QFP32(single wire) [CX3050]  
R5F212K2SDFP@QFP32(UART ISP) [CX0001]  
R5F212K2SDFP@QFP32(UART mode) [CX3050]  
R5F212K2SNFP@QFP32 [CX3061]  
R5F212K2SNFP@QFP32(single ISP) [CX0001]  
R5F212K2SNFP@QFP32(single wire) [CX3050]  
R5F212K2SNFP@QFP32(UART ISP) [CX0001]  
R5F212K2SNFP@QFP32(UART mode) [CX3050]  
R5F212K4SDFP@QFP32 [CX3061]  
R5F212K4SDFP@QFP32(single ISP) [CX0001]  
R5F212K4SDFP@QFP32(single wire) [CX3050]  
R5F212K4SDFP@QFP32(UART ISP) [CX0001]  
R5F212K4SDFP@QFP32(UART mode) [CX3050]  
R5F212K4SNFP@QFP32 [CX3061]  
R5F212K4SNFP@QFP32(single ISP) [CX0001]  
R5F212K4SNFP@QFP32(single wire) [CX3050]  
R5F212K4SNFP@QFP32(UART ISP) [CX0001]  
R5F212K4SNFP@QFP32(UART mode) [CX3050]  
R5F212L2SDFP@QFP32 [CX3061]  
R5F212L2SDFP@QFP32(single ISP) [CX0001]  
R5F212L2SDFP@QFP32(single wire) [CX3050]  
R5F212L2SDFP@QFP32(UART ISP) [CX0001]  
R5F212L2SDFP@QFP32(UART mode) [CX3050]  
R5F212L2SNFP@QFP32 [CX3061]  
R5F212L2SNFP@QFP32(single ISP) [CX0001]  
R5F212L2SNFP@QFP32(single wire) [CX3050]  
R5F212L2SNFP@QFP32(UART ISP) [CX0001]  
R5F212L2SNFP@QFP32(UART mode) [CX3050]  
R5F212L4SDFP@QFP32 [CX3061]  
R5F212L4SDFP@QFP32(single ISP) [CX0001]  
R5F212L4SDFP@QFP32(single wire) [CX3050]  
R5F212L4SDFP@QFP32(UART ISP) [CX0001]

R5F212L4SDFP@QFP32(UART mode) [CX3050]  
R5F212L4SNFP@QFP32 [CX3061]  
R5F212L4SNFP@QFP32(single ISP) [CX0001]  
R5F212L4SNFP@QFP32(single wire) [CX3050]  
R5F212L4SNFP@QFP32(UART ISP) [CX0001]  
R5F212L4SNFP@QFP32(UART mode) [CX3050]  
R5F21331ADFP [CX3001] R5F21331ANFP [CX3001]  
R5F21331CDFP [CX3001] R5F21331CNFP [CX3001]  
R5F21331DDFP [CX3001] R5F21331DNFP [CX3001]  
R5F21331MDFP [CX3001] R5F21331MNFP [CX3001]  
R5F21332ADFP [CX3001] R5F21332ANFP [CX3001]  
R5F21332CDFP [CX3001] R5F21332CNFP [CX3001]  
R5F21332DDFP [CX3001] R5F21332DNFP [CX3001]  
R5F21332MDFP [CX3001] R5F21332MNFP [CX3001]  
R5F21334ADFP [CX3001] R5F21334ANFP [CX3001]  
R5F21334CDFP [CX3001] R5F21334CNFP [CX3001]  
R5F21334DDFP [CX3001] R5F21334DNFP [CX3001]  
R5F21334MDFP [CX3001] R5F21334MNFP [CX3001]  
R5F21334TDFP [CX3001] R5F21334TNFP [CX3001]  
R5F21335ADFP [CX3001] R5F21335ANFP [CX3001]  
R5F21335CDFP [CX3001] R5F21335CNFP [CX3001]  
R5F21335DDFP [CX3001] R5F21335DNFP [CX3001]  
R5F21335MDFP [CX3001] R5F21335MNFP [CX3001]  
R5F21335TDFP [CX3001] R5F21335TNFP [CX3001]  
R5F21336ADFP [CX3001] R5F21336ANFP [CX3001]  
R5F21336CDFP [CX3001] R5F21336CNFP [CX3001]  
R5F21336DDFP [CX3001] R5F21336DNFP [CX3001]  
R5F21336MDFP [CX3001] R5F21336MNFP [CX3001]  
R5F21336TDFP [CX3001] R5F21336TNFP [CX3001]  
R5F21346EJFP@QFP48 [CX3007] R5F21346EKFP@QFP48 [CX3007]  
R5F21346FJFP@QFP48 [CX3007] R5F21346FKFP@QFP48 [CX3007]  
R5F21346GJFP@QFP48 [CX3007] R5F21346GKFP@QFP48 [CX3007]  
R5F21346HJFP@QFP48 [CX3007] R5F21346HKFP@QFP48 [CX3007]  
R5F21346WJFP [CX3007] R5F21346WKFP [CX3007]  
R5F21346XJFP [CX3007] R5F21346XKFP [CX3007]  
R5F21347EJFP@QFP48 [CX3007] R5F21347EKFP@QFP48 [CX3007]  
R5F21347FJFP@QFP48 [CX3007] R5F21347FKFP@QFP48 [CX3007]  
R5F21347GJFP@QFP48 [CX3007] R5F21347GKFP@QFP48 [CX3007]  
R5F21347HJFP@QFP48 [CX3007] R5F21347HKFP@QFP48 [CX3007]  
R5F21347WJFP [CX3007] R5F21347WKFP [CX3007]  
R5F21347XJFP [CX3007] R5F21347XKFP [CX3007]  
R5F21348EJFP@QFP48 [CX3007] R5F21348EKFP@QFP48 [CX3007]  
R5F21348FJFP@QFP48 [CX3007] R5F21348FKFP@QFP48 [CX3007]  
R5F21348GJFP@QFP48 [CX3007] R5F21348GKFP@QFP48 [CX3007]  
R5F21348HJFP@QFP48 [CX3007] R5F21348HKFP@QFP48 [CX3007]  
R5F21348WJFP [CX3007] R5F21348WKFP [CX3007]  
R5F21348XJFP [CX3007] R5F21348XKFP [CX3007]  
R5F2134AEJFP@QFP48 [CX3007] R5F2134AEKFP@QFP48 [CX3007]  
R5F2134AFJFP@QFP48 [CX3007] R5F2134AFKFP@QFP48 [CX3007]  
R5F2134AGJFP@QFP48 [CX3007] R5F2134AGKFP@QFP48 [CX3007]  
R5F2134AHJFP@QFP48 [CX3007] R5F2134AHKFP@QFP48 [CX3007]  
R5F2134AWJFP [CX3007] R5F2134AWKFP [CX3007]  
R5F2134AXJFP [CX3007] R5F2134AXKFP [CX3007]  
R5F2134CEJFP@QFP48 [CX3007] R5F2134CEKFP@QFP48 [CX3007]  
R5F2134CFJFP@QFP48 [CX3007] R5F2134CFKFP@QFP48 [CX3007]  
R5F2134CGJFP@QFP48 [CX3007] R5F2134CGKFP@QFP48 [CX3007]  
R5F2134CHJFP@QFP48 [CX3007] R5F2134CHKFP@QFP48 [CX3007]  
R5F2134CWJFP [CX3007] R5F2134CWKFP [CX3007]  
R5F2134CXJFP [CX3007] R5F2134CXKFP [CX3007]

R5F21354ADFP@QFP52(single wire) [CX3010]  
R5F21354ANFP@QFP52(single wire) [CX3010]  
R5F21354BDFP@QFP52(single wire) [CX3010]  
R5F21354BNFP@QFP52(single wire) [CX3010]  
R5F21354CDFP@QFP52(single wire) [CX3010]  
R5F21354CNFP@QFP52(single wire) [CX3010]  
R5F21355ADFP@QFP52(single wire) [CX3010]  
R5F21355ANFP@QFP52(single wire) [CX3010]  
R5F21355BDFP@QFP52(single wire) [CX3010]  
R5F21355BNFP@QFP52(single wire) [CX3010]  
R5F21355CDFP@QFP52(single wire) [CX3010]  
R5F21355CNFP@QFP52(single wire) [CX3010]  
R5F21356ADFP@QFP52(single wire) [CX3010]  
R5F21356ANFP@QFP52(single wire) [CX3010]  
R5F21356BDFP@QFP52(single wire) [CX3010]  
R5F21356BNFP@QFP52(single wire) [CX3010]  
R5F21356CDFP@QFP52(single wire) [CX3010]  
R5F21356CNFP@QFP52(single wire) [CX3010]  
R5F21357ADFP@QFP52(single wire) [CX3010]  
R5F21357ANFP@QFP52(single wire) [CX3010]  
R5F21357BDFP@QFP52(single wire) [CX3010]  
R5F21357BNFP@QFP52(single wire) [CX3010]  
R5F21357CDFP@QFP52(single wire) [CX3010]  
R5F21357CNFP@QFP52(single wire) [CX3010]  
R5F21358ADFP@QFP52(single wire) [CX3010]  
R5F21358ANFP@QFP52(single wire) [CX3010]  
R5F21358BDFP@QFP52(single wire) [CX3010]  
R5F21358BNFP@QFP52(single wire) [CX3010]  
R5F21358CDFP@QFP52(single wire) [CX3010]  
R5F21358CNFP@QFP52(single wire) [CX3010]  
R5F2135AADFP@QFP52(single wire) [CX3010]  
R5F2135AANFP@QFP52(single wire) [CX3010]  
R5F2135ABDFP@QFP52(single wire) [CX3010]  
R5F2135ABNFP@QFP52(single wire) [CX3010]  
R5F2135ACDFP@QFP52(single wire) [CX3010]  
R5F2135ACNFP@QFP52(single wire) [CX3010]  
R5F2135CADFP@QFP52(single wire) [CX3010]  
R5F2135CANFP@QFP52(single wire) [CX3010]  
R5F2135CBDFP@QFP52(single wire) [CX3010]  
R5F2135CBNFP@QFP52(single wire) [CX3010]  
R5F2135CCDFP@QFP52(single wire) [CX3010]  
R5F2135CCNFP@QFP52(single wire) [CX3010]  
R5F21364ADFA [CX3013] R5F21364ADFP [CX3011]  
R5F21364ANFA [CX3013] R5F21364ANFP [CX3011]  
R5F21364CDFA [CX3013] R5F21364CDFP [CX3011]  
R5F21364CNFA [CX3013] R5F21364CNFP [CX3011]  
R5F21365ADFA [CX3013] R5F21365ADFP [CX3011]  
R5F21365ANFA [CX3013] R5F21365ANFP [CX3011]  
R5F21365CDFA [CX3013] R5F21365CDFP [CX3011]  
R5F21365CNFA [CX3013] R5F21365CNFP [CX3011]  
R5F21366ADFA [CX3013] R5F21366ADFP [CX3011]  
R5F21366ANFA [CX3013] R5F21366ANFP [CX3011]  
R5F21366CDFA [CX3013] R5F21366CDFP [CX3011]  
R5F21366CNFA [CX3013] R5F21366CNFP [CX3011]  
R5F21367ADFA [CX3013] R5F21367ADFP [CX3011]  
R5F21367ANFA [CX3013] R5F21367ANFP [CX3011]  
R5F21367CDFA [CX3013] R5F21367CDFP [CX3011]  
R5F21367CNFA [CX3013] R5F21367CNFP [CX3011]  
R5F21368ADFA [CX3013] R5F21368ADFP [CX3011]

R5F21368ANFA [CX3013]	R5F21368ANFP [CX3011]
R5F21368CDFA [CX3013]	R5F21368CDFP [CX3011]
R5F21368CNFA [CX3013]	R5F21368CNFP [CX3011]
R5F2136AADFA [CX3013]	R5F2136AADFP [CX3011]
R5F2136AANFA [CX3013]	R5F2136AANFP [CX3011]
R5F2136ACDFA [CX3013]	R5F2136ACDFP [CX3011]
R5F2136ACNFA [CX3013]	R5F2136ACNFP [CX3011]
R5F2136CADFA [CX3013]	R5F2136CADFP [CX3011]
R5F2136CANFA [CX3013]	R5F2136CANFP [CX3011]
R5F2136CCDFA [CX3013]	R5F2136CCDFP [CX3011]
R5F2136CCNFA [CX3013]	R5F2136CCNFP [CX3011]
R5F213G1DDSP [CX1026]	R5F213G1DNSP [CX1026]
R5F213G2DDSP [CX1026]	R5F213G2DNSP [CX1026]
R5F213G4DDSP [CX1026]	R5F213G4DNSP [CX1026]
R5F213G5DDSP [CX1026]	R5F213G5DNSP [CX1026]
R5F213G6DDSP [CX1026]	R5F213G6DNSP [CX1026]
R5F2L357ADFP@QFP52 [CX3010]	
R5F2L357ADFP@QFP52(single wire) [CX3010]	
R5F2L357ANFP@QFP52 [CX3010]	
R5F2L357ANFP@QFP52(single wire) [CX3010]	
R5F2L357BDFP@QFP52 [CX3010]	
R5F2L357BDFP@QFP52(single wire) [CX3010]	
R5F2L357BNFP@QFP52 [CX3010]	
R5F2L357BNFP@QFP52(single wire) [CX3010]	
R5F2L357CDFP@QFP52 [CX3010]	
R5F2L357CDFP@QFP52(single wire) [CX3010]	
R5F2L357CNFP@QFP52 [CX3010]	
R5F2L357CNFP@QFP52(single wire) [CX3010]	
R5F2L358ADFP@QFP52 [CX3010]	
R5F2L358ADFP@QFP52(single wire) [CX3010]	
R5F2L358ANFP@QFP52 [CX3010]	
R5F2L358ANFP@QFP52(single wire) [CX3010]	
R5F2L358BDFP@QFP52 [CX3010]	
R5F2L358BDFP@QFP52(single wire) [CX3010]	
R5F2L358BNFP@QFP52 [CX3010]	
R5F2L358BNFP@QFP52(single wire) [CX3010]	
R5F2L358CDFP@QFP52 [CX3010]	
R5F2L358CDFP@QFP52(single wire) [CX3010]	
R5F2L358CNFP@QFP52 [CX3010]	
R5F2L358CNFP@QFP52(single wire) [CX3010]	
R5F2L35AADFP@QFP52 [CX3010]	
R5F2L35AADFP@QFP52(single wire) [CX3010]	
R5F2L35AANFP@QFP52 [CX3010]	
R5F2L35AANFP@QFP52(single wire) [CX3010]	
R5F2L35ABDFP@QFP52 [CX3010]	
R5F2L35ABDFP@QFP52(single wire) [CX3010]	
R5F2L35ABNFP@QFP52 [CX3010]	
R5F2L35ABNFP@QFP52(single wire) [CX3010]	
R5F2L35ACDFP@QFP52 [CX3010]	
R5F2L35ACDFP@QFP52(single wire) [CX3010]	
R5F2L35ACNFP@QFP52 [CX3010]	
R5F2L35ACNFP@QFP52(single wire) [CX3010]	
R5F2L35CADFP@QFP52 [CX3010]	
R5F2L35CADFP@QFP52(single wire) [CX3010]	
R5F2L35CANFP@QFP52 [CX3010]	
R5F2L35CANFP@QFP52(single wire) [CX3010]	
R5F2L35CBDFP@QFP52 [CX3010]	
R5F2L35CBDFP@QFP52(single wire) [CX3010]	
R5F2L35CBNFP@QFP52 [CX3010]	

R5F2L35CBNFP@QFP52(single wire) [CX3010]  
R5F2L35CCDFP@QFP52 [CX3010]  
R5F2L35CCDFP@QFP52(single wire) [CX3010]  
R5F2L35CCNFP@QFP52 [CX3010]  
R5F2L35CCNFP@QFP52(single wire) [CX3010]  
R5F2L367ADFA@QFP64 [CX3013]  
R5F2L367ADFA@QFP64(single wire) [CX3013]  
R5F2L367ADFP@QFP64 [CX3011]  
R5F2L367ADFP@QFP64(single wire) [CX3011]  
R5F2L367ANFA@QFP64 [CX3013]  
R5F2L367ANFA@QFP64(single wire) [CX3013]  
R5F2L367ANFP@QFP64 [CX3011]  
R5F2L367ANFP@QFP64(single wire) [CX3011]  
R5F2L367BDFA@QFP64 [CX3013]  
R5F2L367BDFA@QFP64(single wire) [CX3013]  
R5F2L367BDFP@QFP64 [CX3011]  
R5F2L367BDFP@QFP64(single wire) [CX3011]  
R5F2L367BNFA@QFP64 [CX3013]  
R5F2L367BNFA@QFP64(single wire) [CX3013]  
R5F2L367BNFP@QFP64 [CX3011]  
R5F2L367BNFP@QFP64(single wire) [CX3011]  
R5F2L367CDFA@QFP64 [CX3013]  
R5F2L367CDFA@QFP64(single wire) [CX3013]  
R5F2L367CDFP@QFP64 [CX3011]  
R5F2L367CDFP@QFP64(single wire) [CX3011]  
R5F2L367CNFA@QFP64 [CX3013]  
R5F2L367CNFA@QFP64(single wire) [CX3013]  
R5F2L367CNFP@QFP64 [CX3011]  
R5F2L367CNFP@QFP64(single wire) [CX3011]  
R5F2L368ADFA@QFP64 [CX3013]  
R5F2L368ADFA@QFP64(single wire) [CX3013]  
R5F2L368ADFP@QFP64 [CX3011]  
R5F2L368ADFP@QFP64(single wire) [CX3011]  
R5F2L368ANFA@QFP64 [CX3013]  
R5F2L368ANFA@QFP64(single wire) [CX3013]  
R5F2L368ANFP@QFP64 [CX3011]  
R5F2L368ANFP@QFP64(single wire) [CX3011]  
R5F2L368BDFA@QFP64 [CX3013]  
R5F2L368BDFA@QFP64(single wire) [CX3013]  
R5F2L368BDFP@QFP64 [CX3011]  
R5F2L368BDFP@QFP64(single wire) [CX3011]  
R5F2L368BNFA@QFP64 [CX3013]  
R5F2L368BNFA@QFP64(single wire) [CX3013]  
R5F2L368BNFP@QFP64 [CX3011]  
R5F2L368BNFP@QFP64(single wire) [CX3011]  
R5F2L368CDFA@QFP64 [CX3013]  
R5F2L368CDFA@QFP64(single wire) [CX3013]  
R5F2L368CDFP@QFP64 [CX3011]  
R5F2L368CDFP@QFP64(single wire) [CX3011]  
R5F2L368CNFA@QFP64 [CX3013]  
R5F2L368CNFA@QFP64(single wire) [CX3013]  
R5F2L368CNFP@QFP64 [CX3011]  
R5F2L368CNFP@QFP64(single wire) [CX3011]  
R5F2L36AADFA@QFP64 [CX3013]  
R5F2L36AADFA@QFP64(single wire) [CX3013]  
R5F2L36AADFP@QFP64 [CX3011]  
R5F2L36AADFP@QFP64(single wire) [CX3011]  
R5F2L36AANFA@QFP64 [CX3013]  
R5F2L36AANFA@QFP64(single wire) [CX3013]



R5F2L36AANFP@QFP64 [CX3011]  
R5F2L36AANFP@QFP64(single wire) [CX3011]  
R5F2L36ABDFA@QFP64 [CX3013]  
R5F2L36ABDFA@QFP64(single wire) [CX3013]  
R5F2L36ABDFP@QFP64 [CX3011]  
R5F2L36ABDFP@QFP64(single wire) [CX3011]  
R5F2L36ABNFA@QFP64 [CX3013]  
R5F2L36ABNFA@QFP64(single wire) [CX3013]  
R5F2L36ABNFP@QFP64 [CX3011]  
R5F2L36ABNFP@QFP64(single wire) [CX3011]  
R5F2L36ACDFA@QFP64 [CX3013]  
R5F2L36ACDFA@QFP64(single wire) [CX3013]  
R5F2L36ACDFP@QFP64 [CX3011]  
R5F2L36ACDFP@QFP64(single wire) [CX3011]  
R5F2L36ACNFA@QFP64 [CX3013]  
R5F2L36ACNFA@QFP64(single wire) [CX3013]  
R5F2L36ACNFP@QFP64 [CX3011]  
R5F2L36ACNFP@QFP64(single wire) [CX3011]  
R5F2L36CADFA@QFP64 [CX3013]  
R5F2L36CADFA@QFP64(single wire) [CX3013]  
R5F2L36CADFP@QFP64 [CX3011]  
R5F2L36CADFP@QFP64(single wire) [CX3011]  
R5F2L36CANFA@QFP64 [CX3013]  
R5F2L36CANFA@QFP64(single wire) [CX3013]  
R5F2L36CANFP@QFP64 [CX3011]  
R5F2L36CANFP@QFP64(single wire) [CX3011]  
R5F2L36CBDFA@QFP64 [CX3013]  
R5F2L36CBDFA@QFP64(single wire) [CX3013]  
R5F2L36CBDFP@QFP64 [CX3011]  
R5F2L36CBDFP@QFP64(single wire) [CX3011]  
R5F2L36CBNFA@QFP64 [CX3013]  
R5F2L36CBNFA@QFP64(single wire) [CX3013]  
R5F2L36CBNFP@QFP64 [CX3011]  
R5F2L36CBNFP@QFP64(single wire) [CX3011]  
R5F2L36CCDFA@QFP64 [CX3013]  
R5F2L36CCDFA@QFP64(single wire) [CX3013]  
R5F2L36CCDFP@QFP64 [CX3011]  
R5F2L36CCDFP@QFP64(single wire) [CX3011]  
R5F2L36CCNFA@QFP64 [CX3013]  
R5F2L36CCNFA@QFP64(single wire) [CX3013]  
R5F2L36CCNFP@QFP64 [CX3011]  
R5F2L36CCNFP@QFP64(single wire) [CX3011]  
R5F2L387ADFA@QFP80 [CX3018]  
R5F2L387ADFA@QFP80(single wire) [CX3018]  
R5F2L387ADFP@QFP80 [CX3016]  
R5F2L387ADFP@QFP80(single wire) [CX3016]  
R5F2L387ANFA@QFP80 [CX3018]  
R5F2L387ANFA@QFP80(single wire) [CX3018]  
R5F2L387ANFP@QFP80 [CX3016]  
R5F2L387ANFP@QFP80(single wire) [CX3016]  
R5F2L387BDFA@QFP80 [CX3018]  
R5F2L387BDFA@QFP80(single wire) [CX3018]  
R5F2L387BDFP@QFP80 [CX3016]  
R5F2L387BDFP@QFP80(single wire) [CX3016]  
R5F2L387BNFA@QFP80 [CX3018]  
R5F2L387BNFA@QFP80(single wire) [CX3018]  
R5F2L387BNFP@QFP80 [CX3016]  
R5F2L387BNFP@QFP80(single wire) [CX3016]  
R5F2L387CDFA@QFP80 [CX3018]

R5F2L387CDFA@QFP80(single wire) [CX3018]  
R5F2L387CDFP@QFP80 [CX3016]  
R5F2L387CDFP@QFP80(single wire) [CX3016]  
R5F2L387CNFA@QFP80 [CX3018]  
R5F2L387CNFA@QFP80(single wire) [CX3018]  
R5F2L387CNFP@QFP80 [CX3016]  
R5F2L387CNFP@QFP80(single wire) [CX3016]  
R5F2L388ADFA@QFP80 [CX3018]  
R5F2L388ADFA@QFP80(single wire) [CX3018]  
R5F2L388ADFP@QFP80 [CX3016]  
R5F2L388ADFP@QFP80(single wire) [CX3016]  
R5F2L388ANFA@QFP80 [CX3018]  
R5F2L388ANFA@QFP80(single wire) [CX3018]  
R5F2L388ANFP@QFP80 [CX3016]  
R5F2L388ANFP@QFP80(single wire) [CX3016]  
R5F2L388BDFA@QFP80 [CX3018]  
R5F2L388BDFA@QFP80(single wire) [CX3018]  
R5F2L388BDFP@QFP80 [CX3016]  
R5F2L388BDFP@QFP80(single wire) [CX3016]  
R5F2L388BNFA@QFP80 [CX3018]  
R5F2L388BNFA@QFP80(single wire) [CX3018]  
R5F2L388BNFP@QFP80 [CX3016]  
R5F2L388BNFP@QFP80(single wire) [CX3016]  
R5F2L388CDFA@QFP80 [CX3018]  
R5F2L388CDFA@QFP80(single wire) [CX3018]  
R5F2L388CDFP@QFP80 [CX3016]  
R5F2L388CDFP@QFP80(single wire) [CX3016]  
R5F2L388CNFA@QFP80 [CX3018]  
R5F2L388CNFA@QFP80(single wire) [CX3018]  
R5F2L388CNFP@QFP80 [CX3016]  
R5F2L388CNFP@QFP80(single wire) [CX3016]  
R5F2L38AADFA@QFP80 [CX3018]  
R5F2L38AADFA@QFP80(single wire) [CX3018]  
R5F2L38AADFP@QFP80 [CX3016]  
R5F2L38AADFP@QFP80(single wire) [CX3016]  
R5F2L38AANFA@QFP80 [CX3018]  
R5F2L38AANFA@QFP80(single wire) [CX3018]  
R5F2L38AANFP@QFP80 [CX3016]  
R5F2L38AANFP@QFP80(single wire) [CX3016]  
R5F2L38ABDFA@QFP80 [CX3018]  
R5F2L38ABDFA@QFP80(single wire) [CX3018]  
R5F2L38ABDFP@QFP80 [CX3016]  
R5F2L38ABDFP@QFP80(single wire) [CX3016]  
R5F2L38ABNFA@QFP80 [CX3018]  
R5F2L38ABNFA@QFP80(single wire) [CX3018]  
R5F2L38ABNFP@QFP80 [CX3016]  
R5F2L38ABNFP@QFP80(single wire) [CX3016]  
R5F2L38ACDFA@QFP80 [CX3018]  
R5F2L38ACDFA@QFP80(single wire) [CX3018]  
R5F2L38ACDFP@QFP80 [CX3016]  
R5F2L38ACDFP@QFP80(single wire) [CX3016]  
R5F2L38ACNFA@QFP80 [CX3018]  
R5F2L38ACNFA@QFP80(single wire) [CX3018]  
R5F2L38ACNFP@QFP80 [CX3016]  
R5F2L38ACNFP@QFP80(single wire) [CX3016]  
R5F2L38CADFA@QFP80 [CX3018]  
R5F2L38CADFA@QFP80(single wire) [CX3018]  
R5F2L38CADFP@QFP80 [CX3016]  
R5F2L38CADFP@QFP80(single wire) [CX3016]

R5F2L38CANFA@QFP80 [CX3018]  
R5F2L38CANFA@QFP80(single wire) [CX3018]  
R5F2L38CANFP@QFP80 [CX3016]  
R5F2L38CANFP@QFP80(single wire) [CX3016]  
R5F2L38CBDFA@QFP80 [CX3018]  
R5F2L38CBDFA@QFP80(single wire) [CX3018]  
R5F2L38CBDFP@QFP80 [CX3016]  
R5F2L38CBDFP@QFP80(single wire) [CX3016]  
R5F2L38CBNFA@QFP80 [CX3018]  
R5F2L38CBNFA@QFP80(single wire) [CX3018]  
R5F2L38CBNFP@QFP80 [CX3016]  
R5F2L38CBNFP@QFP80(single wire) [CX3016]  
R5F2L38CCDFA@QFP80 [CX3018]  
R5F2L38CCDFA@QFP80(single wire) [CX3018]  
R5F2L38CCDFP@QFP80 [CX3016]  
R5F2L38CCDFP@QFP80(single wire) [CX3016]  
R5F2L38CCNFA@QFP80 [CX3018]  
R5F2L38CCNFA@QFP80(single wire) [CX3018]  
R5F2L38CCNFP@QFP80 [CX3016]  
R5F2L38CCNFP@QFP80(single wire) [CX3016]  
R5F2L3A7ADFA@PQFP100 [CX3023]  
R5F2L3A7ADFA@PQFP100(single) [CX3023]  
R5F2L3A7ADFP@PQFP100 [CX3021]  
R5F2L3A7ADFP@PQFP100(single) [CX3021]  
R5F2L3A7ANFA@PQFP100 [CX3023]  
R5F2L3A7ANFA@PQFP100(single) [CX3023]  
R5F2L3A7ANFP@PQFP100 [CX3021]  
R5F2L3A7ANFP@PQFP100(single) [CX3021]  
R5F2L3A7BDFA@PQFP100 [CX3023]  
R5F2L3A7BDFA@PQFP100(single) [CX3023]  
R5F2L3A7BDFP@PQFP100 [CX3021]  
R5F2L3A7BDFP@PQFP100(single) [CX3021]  
R5F2L3A7BNFA@PQFP100 [CX3023]  
R5F2L3A7BNFA@PQFP100(single) [CX3023]  
R5F2L3A7BNFP@PQFP100 [CX3021]  
R5F2L3A7BNFP@PQFP100(single) [CX3021]  
R5F2L3A7CDFA@PQFP100 [CX3023]  
R5F2L3A7CDFA@PQFP100(single) [CX3023]  
R5F2L3A7CDFP@PQFP100 [CX3021]  
R5F2L3A7CDFP@PQFP100(single) [CX3021]  
R5F2L3A7CNFA@PQFP100 [CX3023]  
R5F2L3A7CNFA@PQFP100(single) [CX3023]  
R5F2L3A7CNFP@PQFP100 [CX3021]  
R5F2L3A7CNFP@PQFP100(single) [CX3021]  
R5F2L3A8ADFA@PQFP100 [CX3023]  
R5F2L3A8ADFA@PQFP100(single) [CX3023]  
R5F2L3A8ADFP@PQFP100 [CX3021]  
R5F2L3A8ADFP@PQFP100(single) [CX3021]  
R5F2L3A8ANFA@PQFP100 [CX3023]  
R5F2L3A8ANFA@PQFP100(single) [CX3023]  
R5F2L3A8ANFP@PQFP100 [CX3021]  
R5F2L3A8ANFP@PQFP100(single) [CX3021]  
R5F2L3A8BDFA@PQFP100 [CX3023]  
R5F2L3A8BDFA@PQFP100(single) [CX3023]  
R5F2L3A8BDFP@PQFP100 [CX3021]  
R5F2L3A8BDFP@PQFP100(single) [CX3021]  
R5F2L3A8BNFA@PQFP100 [CX3023]  
R5F2L3A8BNFA@PQFP100(single) [CX3023]  
R5F2L3A8BNFP@PQFP100 [CX3021]

R5F2L3A8BNFP@PQFP100(single) [CX3021]  
R5F2L3A8CDFA@PQFP100 [CX3023]  
R5F2L3A8CDFA@PQFP100(single) [CX3023]  
R5F2L3A8CDFP@PQFP100 [CX3021]  
R5F2L3A8CDFP@PQFP100(single) [CX3021]  
R5F2L3A8CNFA@PQFP100 [CX3023]  
R5F2L3A8CNFA@PQFP100(single) [CX3023]  
R5F2L3A8CNFP@PQFP100 [CX3021]  
R5F2L3A8CNFP@PQFP100(single) [CX3021]  
R5F2L3AAADFA@PQFP100 [CX3023]  
R5F2L3AAADFA@PQFP100(single) [CX3023]  
R5F2L3AAADFP@PQFP100 [CX3021]  
R5F2L3AAADFP@PQFP100(single) [CX3021]  
R5F2L3AAANFA@PQFP100 [CX3023]  
R5F2L3AAANFA@PQFP100(single) [CX3023]  
R5F2L3AAANFP@PQFP100 [CX3021]  
R5F2L3AAANFP@PQFP100(single) [CX3021]  
R5F2L3AABDFA@PQFP100 [CX3023]  
R5F2L3AABDFA@PQFP100(single) [CX3023]  
R5F2L3AABDFP@PQFP100 [CX3021]  
R5F2L3AABDFP@PQFP100(single) [CX3021]  
R5F2L3AABNFA@PQFP100 [CX3023]  
R5F2L3AABNFA@PQFP100(single) [CX3023]  
R5F2L3AABNFP@PQFP100 [CX3021]  
R5F2L3AABNFP@PQFP100(single) [CX3021]  
R5F2L3AACDFA@PQFP100 [CX3023]  
R5F2L3AACDFA@PQFP100(single) [CX3023]  
R5F2L3AACDFP@PQFP100 [CX3021]  
R5F2L3AACDFP@PQFP100(single) [CX3021]  
R5F2L3AACNFA@PQFP100 [CX3023]  
R5F2L3AACNFA@PQFP100(single) [CX3023]  
R5F2L3AACNFP@PQFP100 [CX3021]  
R5F2L3AACNFP@PQFP100(single) [CX3021]  
R5F2L3ACADFA@PQFP100 [CX3023]  
R5F2L3ACADFA@PQFP100(single) [CX3023]  
R5F2L3ACADFP@PQFP100 [CX3021]  
R5F2L3ACADFP@PQFP100(single) [CX3021]  
R5F2L3ACANFA@PQFP100 [CX3023]  
R5F2L3ACANFA@PQFP100(single) [CX3023]  
R5F2L3ACANFP@PQFP100 [CX3021]  
R5F2L3ACANFP@PQFP100(single) [CX3021]  
R5F2L3ACBDFA@PQFP100 [CX3023]  
R5F2L3ACBDFA@PQFP100(single) [CX3023]  
R5F2L3ACBDFP@PQFP100 [CX3021]  
R5F2L3ACBDFP@PQFP100(single) [CX3021]  
R5F2L3ACBNFA@PQFP100 [CX3023]  
R5F2L3ACBNFA@PQFP100(single) [CX3023]  
R5F2L3ACBNFP@PQFP100 [CX3021]  
R5F2L3ACBNFP@PQFP100(single) [CX3021]  
R5F2L3ACCDFA@PQFP100 [CX3023]  
R5F2L3ACCDFA@PQFP100(single) [CX3023]  
R5F2L3ACCDFP@PQFP100 [CX3021]  
R5F2L3ACCDFP@PQFP100(single) [CX3021]  
R5F2L3ACCNFA@PQFP100 [CX3023]  
R5F2L3ACCNFA@PQFP100(single) [CX3023]  
R5F2L3ACCNFP@PQFP100 [CX3021]  
R5F2L3ACCNFP@PQFP100(single) [CX3021]  
R5F2M110ADDD(single) [CX0001]  
R5F2M110ADSP@TSSOP14(single) [CX1000]

R5F2M110ANDD(single) [CX0001]  
R5F2M110ANSP@TSSOP14(single) [CX1000]  
R5F2M111ADDD(single) [CX0001]  
R5F2M111ADSP@TSSOP14(single) [CX1000]  
R5F2M111ANDD(single) [CX0001]  
R5F2M111ANSP@TSSOP14(single) [CX1000]  
R5F2M112ADDD(single) [CX0001]  
R5F2M112ADSP@TSSOP14(single) [CX1000]  
R5F2M112ANDD(single) [CX0001]  
R5F2M112ANSP@TSSOP14(single) [CX1000]  
R5F2M120ADDD(single) [CX0001]  
R5F2M120ADSP@TSSOP20(single) [CX1000]  
R5F2M120ANDD(single) [CX0001]  
R5F2M120ANSP@TSSOP20(single) [CX1000]  
R5F2M121ADDD(single) [CX0001]  
R5F2M121ADSP@TSSOP20(single) [CX1000]  
R5F2M121ANDD(single) [CX0001]  
R5F2M121ANSP@TSSOP20(single) [CX1000]  
R5F2M122ADDD(single) [CX0001]  
R5F2M122ADSP@TSSOP20(single) [CX1000]  
R5F2M122ANDD(single) [CX0001]  
R5F2M122ANSP@TSSOP20(single) [CX1000]  
R5F35623JFE [CX3016] R5F35623KFE [CX3016]  
R5F35626JFE [CX3016] R5F35626KFE [CX3016]  
R5F3562EJFE [CX3016] R5F3562EKFE [CX3016]  
R5F35630JFF [CX3011] R5F35630KFF [CX3011]  
R5F35633JFF [CX3011] R5F35633KFF [CX3011]  
R5F35636JFF [CX3011] R5F35636KFF [CX3011]  
R5F3563EJFF [CX3011] R5F3563EKFF [CX3011]  
R5F35L23JFE [CX3016] R5F35L23KFE [CX3016]  
R5F35L26JFE [CX3016] R5F35L26KFE [CX3016]  
R5F35L2EJFE [CX3016] R5F35L2EKFE [CX3016]  
R5F35L30JFF [CX3011] R5F35L30KFF [CX3011]  
R5F35L33JFF [CX3011] R5F35L33KFF [CX3011]  
R5F35L36JFF [CX3011] R5F35L36KFF [CX3011]  
R5F35L3EJFF [CX3011] R5F35L3EKFF [CX3011]  
R5F363A6DFA@PQFP100 [CX3022] R5F363A6DFB@QFP100 [CX3021]  
R5F363A6NFA@PQFP100 [CX3022] R5F363A6NFB@QFP100 [CX3021]  
R5F363AEDFA@PQFP100 [CX3022] R5F363AEDFB@QFP100 [CX3021]  
R5F363AENFA@PQFP100 [CX3022] R5F363AENFB@QFP100 [CX3021]  
R5F363AKDFA@PQFP100 [CX3022] R5F363AKDFB@QFP100 [CX3021]  
R5F363AKNFA@PQFP100 [CX3022] R5F363AKNFB@QFP100 [CX3021]  
R5F363AMDFA@PQFP100 [CX3022] R5F363AMDFB@QFP100 [CX3021]  
R5F363AMNFA@PQFP100 [CX3022] R5F363AMNFB@QFP100 [CX3021]  
R5F36406DFA@PQFP100 [CX3022] R5F36406DFB@QFP100 [CX3021]  
R5F36406NFA@PQFP100 [CX3022] R5F36406NFB@QFP100 [CX3021]  
R5F3640DDFA@PQFP100 [CX3022] R5F3640DDFB@QFP100 [CX3021]  
R5F3640DNFA@PQFP100 [CX3022] R5F3640DNFB@QFP100 [CX3021]  
R5F3640MDFA@PQFP100 [CX3022] R5F3640MDFB@QFP100 [CX3021]  
R5F3640MNFA@PQFP100 [CX3022] R5F3640MNFB@QFP100 [CX3021]  
R5F364A6DFA@PQFP100 [CX3022] R5F364A6DFB@QFP100 [CX3021]  
R5F364A6NFA@PQFP100 [CX3022] R5F364A6NFB@QFP100 [CX3021]  
R5F364AEDFA@PQFP100 [CX3022] R5F364AEDFB@QFP100 [CX3021]  
R5F364AENFA@PQFP100 [CX3022] R5F364AENFB@QFP100 [CX3021]  
R5F364AMDFA@PQFP100 [CX3022] R5F364AMDFB@QFP100 [CX3021]  
R5F364AMNFA@PQFP100 [CX3022] R5F364AMNFB@QFP100 [CX3021]  
R5F36506DFA@PQFP100 [CX3022] R5F36506DFB@QFP100 [CX3021]  
R5F36506NFA@PQFP100 [CX3022] R5F36506NFB@QFP100 [CX3021]  
R5F3650EDFA@PQFP100 [CX3022] R5F3650EDFB@QFP100 [CX3021]

R5F3650ENFA@QFP100 [CX3022] R5F3650ENFB@QFP100 [CX3021]  
R5F3650KDFA@QFP100 [CX3022] R5F3650KDFB@QFP100 [CX3021]  
R5F3650KNFA@QFP100 [CX3022] R5F3650KNFB@QFP100 [CX3021]  
R5F3650MDFA@QFP100 [CX3022] R5F3650MDFB@QFP100 [CX3021]  
R5F3650MNFA@QFP100 [CX3022] R5F3650MNFB@QFP100 [CX3021]  
R5F3650NDFA@QFP100 [CX3022] R5F3650NDFB@QFP100 [CX3021]  
R5F3650NNFA@QFP100 [CX3022] R5F3650NNFB@QFP100 [CX3021]  
R5F3650RDFA@QFP100 [CX3022] R5F3650RDFB@QFP100 [CX3021]  
R5F3650RNFA@QFP100 [CX3022] R5F3650RNFB@QFP100 [CX3021]  
R5F3650TDFA@QFP100 [CX3022] R5F3650TDFB@QFP100 [CX3021]  
R5F3650TNFA@QFP100 [CX3022] R5F3650TNFB@QFP100 [CX3021]  
R5F562TAEDFF [CX3017]  
R5F562TAEDFF@QFP80(serial) [CX3017]  
R5F562TAEDFH [CX3026]  
R5F562TAEDFH@QFP112(serial) [CX3026]  
R5F562TAEDFK@QFP64(serial) [CX3013]  
R5F562TAEDFM@QFP64(serial) [CX3011]  
R5F562TAEDFP [CX3043]  
R5F562TAEDFP@QFP100(serial) [CX3043]  
R5F71242FPV@QFP48(serial) [CX3008]  
R5F71243FPV@QFP48(serial) [CX3008]  
R5F71252FAV@QFP64(serial) [CX3014]  
R5F71252FPV@QFP64(serial) [CX3011]  
R5F71253FAV@QFP64(serial) [CX3014]  
R5F71253FPV@QFP64(serial) [CX3011]  
R5F71374AD80FPV [CX3043] R5F71374AN80FPV [CX3043]  
R5F71424AK64FPV [CX3043] R5F71424BJ80FPV [CX3043]  
R5F71426AK64FPV [CX3043] R5F71426BD80FPV [CX3043]  
R5F71426BJ80FPV [CX3043] R5F71464FPV@QFP80 [CX3017]  
R5F71464FPV@QFP80(serial) [CX3017]  
R5F71474AK64FPV [CX3043] R5F71474BD80FPV [CX3043]  
R5F71474BJ80FPV [CX3043] R5F71475AK64FPV [CX3043]  
R5F71475BD80FPV [CX3043] R5F71475BJ80FPV [CX3043]  
R5F71476AK64FPV [CX3043] R5F71476BD80FPV [CX3043]  
R5F71476BJ80FPV [CX3043] R5G0C314D@SDIP32 [CX0032]  
R5G0C328FA@QFP32 [CX3001]  
R5R0C0B4SP@TSSOP24(single wire) [CX1012]  
R7F01592ESN [CX1033] R7F01692ESN [CX1033]  
R7F0C011B2001DFP [CX3001] R7F0C012B2001DFP [CX3001]  
R7F0C013B2001DFP [CX3001] R7F0C014 [CX3001]  
uPD75P108BCW [CX0064] uPD75P108BDW [CX0064]  
uPD75P108BGF [CX3015] uPD75P108CW [CX0064]  
uPD75P108DW [CX0064] uPD75P108GF [CX3015]  
uPD75P116BCW [CX0064] uPD75P116BDW [CX0064]  
uPD75P116BGF [CX3015] uPD75P116CW [CX0064]  
uPD75P116DW [CX0064] uPD75P116GF [CX3015]  
uPD78F0500AAQS [CX1027] uPD78F0500AAQSA [CX1027]  
uPD78F0500AFC uPD78F0500AMC [CX1027]  
uPD78F0500AMCA [CX1027] uPD78F0500AQS [CX1027]  
uPD78F0500AQSA [CX1027] uPD78F0500FC  
uPD78F0500MC [CX1027] uPD78F0500MCA [CX1027]  
uPD78F0501AAQS [CX1027] uPD78F0501AAQSA [CX1027]  
uPD78F0501AFC uPD78F0501AMC [CX1027]  
uPD78F0501AMCA [CX1027] uPD78F0501AQS [CX1027]  
uPD78F0501AQSA [CX1027] uPD78F0501FC  
uPD78F0501MC [CX1027] uPD78F0501MCA [CX1027]  
uPD78F0502AAQS [CX1027] uPD78F0502AAQSA [CX1027]  
uPD78F0502AFC uPD78F0502AMC [CX1027]  
uPD78F0502AMCA [CX1027] uPD78F0502AQS [CX1027]

uPD78F0502AQSA [CX1027]  
uPD78F0502MC [CX1027]  
uPD78F0503AAQS [CX1027]  
uPD78F0503ADFC  
uPD78F0503ADMCA [CX1027]  
uPD78F0503AMC [CX1027]  
uPD78F0503AQS [CX1027]  
uPD78F0503DFC  
uPD78F0503DMCA [CX1027]  
uPD78F0503MC [CX1027]  
uPD78F0511AGA [CX3047]  
uPD78F0511AGAA2 [CX3047]  
uPD78F0511AGBA [CX3005]  
uPD78F0511AMC [CX1027]  
uPD78F0511GAA [CX3047]  
uPD78F0511GB [CX3005]  
uPD78F0511GBA2 [CX3005]  
uPD78F0512AGA [CX3047]  
uPD78F0512AGAA2 [CX3047]  
uPD78F0512AGBA [CX3005]  
uPD78F0512AMC [CX1027]  
uPD78F0512GAA [CX3047]  
uPD78F0512GB [CX3005]  
uPD78F0512GBA2 [CX3005]  
uPD78F0513ADGA [CX3047]  
uPD78F0513ADGAA2 [CX3047]  
uPD78F0513ADGBA [CX3005]  
uPD78F0513ADMC [CX1027]  
uPD78F0513AGAA [CX3047]  
uPD78F0513AGB [CX3005]  
uPD78F0513AGBA2 [CX3005]  
uPD78F0513DGA [CX3047]  
uPD78F0513DGAA2 [CX3047]  
uPD78F0513DGBA [CX3005]  
uPD78F0513DMC [CX1027]  
uPD78F0513GAA [CX3047]  
uPD78F0513GB [CX3005]  
uPD78F0513GBA2 [CX3005]  
uPD78F0514AGA [CX3047]  
uPD78F0514AGAA2 [CX3047]  
uPD78F0514AGBA [CX3005]  
uPD78F0514AMC [CX1027]  
uPD78F0514GAA [CX3047]  
uPD78F0514GB [CX3005]  
uPD78F0514GBA2 [CX3005]  
uPD78F0515AGA [CX3047]  
uPD78F0515AGAA2 [CX3047]  
uPD78F0515AGBA [CX3005]  
uPD78F0515AMC [CX1027]  
uPD78F0515GAA [CX3047]  
uPD78F0515GB [CX3005]  
uPD78F0515GBA2 [CX3005]  
uPD78F0521AGB [CX3010]  
uPD78F0521AGBA2 [CX3010]  
uPD78F0521GBA [CX3010]  
uPD78F0522AGB [CX3010]  
uPD78F0522AGBA2 [CX3010]  
uPD78F0522GBA [CX3010]  
uPD78F0523ADGB [CX3010]

uPD78F0502FC  
uPD78F0502MCA [CX1027]  
uPD78F0503AAQSA [CX1027]  
uPD78F0503ADMC [CX1027]  
uPD78F0503AFC  
uPD78F0503AMCA [CX1027]  
uPD78F0503AQSA [CX1027]  
uPD78F0503DMC [CX1027]  
uPD78F0503FC  
uPD78F0503MCA [CX1027]  
uPD78F0511AGAA [CX3047]  
uPD78F0511AGB [CX3005]  
uPD78F0511AGBA2 [CX3005]  
uPD78F0511GA [CX3047]  
uPD78F0511GAA2 [CX3047]  
uPD78F0511GBA [CX3005]  
uPD78F0511MC [CX1027]  
uPD78F0512AGAA [CX3047]  
uPD78F0512AGB [CX3005]  
uPD78F0512AGBA2 [CX3005]  
uPD78F0512GA [CX3047]  
uPD78F0512GAA2 [CX3047]  
uPD78F0512GBA [CX3005]  
uPD78F0512MC [CX1027]  
uPD78F0513ADGAA [CX3047]  
uPD78F0513ADGB [CX3005]  
uPD78F0513ADGBA2 [CX3005]  
uPD78F0513AGA [CX3047]  
uPD78F0513AGAA2 [CX3047]  
uPD78F0513AGBA [CX3005]  
uPD78F0513AMC [CX1027]  
uPD78F0513DGAA [CX3047]  
uPD78F0513DGB [CX3005]  
uPD78F0513DGBA2 [CX3005]  
uPD78F0513GA [CX3047]  
uPD78F0513GAA2 [CX3047]  
uPD78F0513GBA [CX3005]  
uPD78F0513MC [CX1027]  
uPD78F0514AGAA [CX3047]  
uPD78F0514AGB [CX3005]  
uPD78F0514AGBA2 [CX3005]  
uPD78F0514GA [CX3047]  
uPD78F0514GAA2 [CX3047]  
uPD78F0514GBA [CX3005]  
uPD78F0514MC [CX1027]  
uPD78F0515AGAA [CX3047]  
uPD78F0515AGB [CX3005]  
uPD78F0515AGBA2 [CX3005]  
uPD78F0515GA [CX3047]  
uPD78F0515GAA2 [CX3047]  
uPD78F0515GBA [CX3005]  
uPD78F0515MC [CX1027]  
uPD78F0521AGBA [CX3010]  
uPD78F0521GB [CX3010]  
uPD78F0521GBA2 [CX3010]  
uPD78F0522AGBA [CX3010]  
uPD78F0522GB [CX3010]  
uPD78F0522GBA2 [CX3010]  
uPD78F0523ADGBA [CX3010]

uPD78F0523ADGBA2 [CX3010]  
uPD78F0523AGBA [CX3010]  
uPD78F0523DGB [CX3010]  
uPD78F0523DGBA2 [CX3010]  
uPD78F0523GBA [CX3010]  
uPD78F0524AGB [CX3010]  
uPD78F0524AGBA2 [CX3010]  
uPD78F0524GBA [CX3010]  
uPD78F0525AGB [CX3010]  
uPD78F0525AGBA2 [CX3010]  
uPD78F0525GBA [CX3010]  
uPD78F0526AGB [CX3010]  
uPD78F0526AGBA2 [CX3010]  
uPD78F0526GBA [CX3010]  
uPD78F0527AGB [CX3010]  
uPD78F0527AGBA2 [CX3010]  
uPD78F0527GBA [CX3010]  
uPD78F0531AGB [CX3011]  
uPD78F0531AGBA2 [CX3011]  
uPD78F0531AGCA [CX3013]  
uPD78F0531AGK [CX3012]  
uPD78F0531AGKA2 [CX3012]  
uPD78F0531GBA [CX3011]  
uPD78F0531GC [CX3013]  
uPD78F0531GCA2 [CX3013]  
uPD78F0531GKA [CX3012]  
uPD78F0532AGB [CX3011]  
uPD78F0532AGBA2 [CX3011]  
uPD78F0532AGCA [CX3013]  
uPD78F0532AGK [CX3012]  
uPD78F0532AGKA2 [CX3012]  
uPD78F0532GBA [CX3011]  
uPD78F0532GC [CX3013]  
uPD78F0532GCA2 [CX3013]  
uPD78F0532GKA [CX3012]  
uPD78F0533ADGB [CX3011]  
uPD78F0533ADGBA2 [CX3011]  
uPD78F0533ADGCA [CX3013]  
uPD78F0533ADGK [CX3012]  
uPD78F0533ADGKA2 [CX3012]  
uPD78F0533AGBA [CX3011]  
uPD78F0533AGC [CX3013]  
uPD78F0533AGCA2 [CX3013]  
uPD78F0533AGKA [CX3012]  
uPD78F0533DGB [CX3011]  
uPD78F0533DGBA2 [CX3011]  
uPD78F0533DGCA [CX3013]  
uPD78F0533DGK [CX3012]  
uPD78F0533DGKA2 [CX3012]  
uPD78F0533GBA [CX3011]  
uPD78F0533GC [CX3013]  
uPD78F0533GCA2 [CX3013]  
uPD78F0533GKA [CX3012]  
uPD78F0534AGB [CX3011]  
uPD78F0534AGBA2 [CX3011]  
uPD78F0534AGCA [CX3013]  
uPD78F0534AGK [CX3012]  
uPD78F0534AGKA2 [CX3012]  
uPD78F0534GBA [CX3011]

uPD78F0523AGB [CX3010]  
uPD78F0523AGBA2 [CX3010]  
uPD78F0523DGBA [CX3010]  
uPD78F0523GB [CX3010]  
uPD78F0523GBA2 [CX3010]  
uPD78F0524AGBA [CX3010]  
uPD78F0524GB [CX3010]  
uPD78F0524GBA2 [CX3010]  
uPD78F0525AGBA [CX3010]  
uPD78F0525GB [CX3010]  
uPD78F0525GBA2 [CX3010]  
uPD78F0526AGBA [CX3010]  
uPD78F0526GB [CX3010]  
uPD78F0526GBA2 [CX3010]  
uPD78F0527AGBA [CX3010]  
uPD78F0527GB [CX3010]  
uPD78F0527GBA2 [CX3010]  
uPD78F0531AGBA [CX3011]  
uPD78F0531AGC [CX3013]  
uPD78F0531AGCA2 [CX3013]  
uPD78F0531AGKA [CX3012]  
uPD78F0531GB [CX3011]  
uPD78F0531GBA2 [CX3011]  
uPD78F0531GCA [CX3013]  
uPD78F0531GK [CX3012]  
uPD78F0531GKA2 [CX3012]  
uPD78F0532AGBA [CX3011]  
uPD78F0532AGC [CX3013]  
uPD78F0532AGCA2 [CX3013]  
uPD78F0532AGKA [CX3012]  
uPD78F0532GB [CX3011]  
uPD78F0532GBA2 [CX3011]  
uPD78F0532GCA [CX3013]  
uPD78F0532GK [CX3012]  
uPD78F0532GKA2 [CX3012]  
uPD78F0533ADGBA [CX3011]  
uPD78F0533ADGC [CX3013]  
uPD78F0533ADGCA2 [CX3013]  
uPD78F0533ADGKA [CX3012]  
uPD78F0533AGB [CX3011]  
uPD78F0533AGBA2 [CX3011]  
uPD78F0533AGCA [CX3013]  
uPD78F0533AGK [CX3012]  
uPD78F0533AGKA2 [CX3012]  
uPD78F0533DGBA [CX3011]  
uPD78F0533DGC [CX3013]  
uPD78F0533DGCA2 [CX3013]  
uPD78F0533DGKA [CX3012]  
uPD78F0533GB [CX3011]  
uPD78F0533GBA2 [CX3011]  
uPD78F0533GCA [CX3013]  
uPD78F0533GK [CX3012]  
uPD78F0533GKA2 [CX3012]  
uPD78F0534AGBA [CX3011]  
uPD78F0534AGC [CX3013]  
uPD78F0534AGCA2 [CX3013]  
uPD78F0534AGKA [CX3012]  
uPD78F0534GB [CX3011]  
uPD78F0534GBA2 [CX3011]



uPD78F0534GC [CX3013]  
uPD78F0534GCA2 [CX3013]  
uPD78F0534GKA [CX3012]  
uPD78F0535AGB [CX3011]  
uPD78F0535AGBA2 [CX3011]  
uPD78F0535AGCA [CX3013]  
uPD78F0535AGK [CX3012]  
uPD78F0535AGKA2 [CX3012]  
uPD78F0535GBA [CX3011]  
uPD78F0535GC [CX3013]  
uPD78F0535GCA2 [CX3013]  
uPD78F0535GKA [CX3012]  
uPD78F0536AGB [CX3011]  
uPD78F0536AGBA2 [CX3011]  
uPD78F0536AGCA [CX3013]  
uPD78F0536AGK [CX3012]  
uPD78F0536AGKA2 [CX3012]  
uPD78F0536GBA [CX3011]  
uPD78F0536GC [CX3013]  
uPD78F0536GCA2 [CX3013]  
uPD78F0536GKA [CX3012]  
uPD78F0537ADGB [CX3011]  
uPD78F0537ADGBA2 [CX3011]  
uPD78F0537ADGCA [CX3013]  
uPD78F0537ADGK [CX3012]  
uPD78F0537ADGKA2 [CX3012]  
uPD78F0537AGBA [CX3011]  
uPD78F0537AGC [CX3013]  
uPD78F0537AGCA2 [CX3013]  
uPD78F0537AGKA [CX3012]  
uPD78F0537DGB [CX3011]  
uPD78F0537DGBA2 [CX3011]  
uPD78F0537DGCA [CX3013]  
uPD78F0537DGK [CX3012]  
uPD78F0537DGKA2 [CX3012]  
uPD78F0537GBA [CX3011]  
uPD78F0537GC [CX3013]  
uPD78F0537GCA2 [CX3013]  
uPD78F0537GKA [CX3012]  
uPD78F0544AGC [CX3017]  
uPD78F0544AGCA2 [CX3017]  
uPD78F0544AGKA [CX3016]  
uPD78F0544GC [CX3017]  
uPD78F0544GCA2 [CX3017]  
uPD78F0544GKA [CX3016]  
uPD78F0545AGC [CX3017]  
uPD78F0545AGCA2 [CX3017]  
uPD78F0545AGKA [CX3016]  
uPD78F0545GC [CX3017]  
uPD78F0545GCA2 [CX3017]  
uPD78F0545GKA [CX3016]  
uPD78F0546AGK [CX3016]  
uPD78F0546AGKA2 [CX3016]  
uPD78F0546GKA [CX3016]  
uPD78F0547ADGC [CX3017]  
uPD78F0547ADGCA2 [CX3017]  
uPD78F0547ADGKA [CX3016]  
uPD78F0547AGC [CX3017]  
uPD78F0547AGCA2 [CX3017]

uPD78F0534GCA [CX3013]  
uPD78F0534GK [CX3012]  
uPD78F0534GKA2 [CX3012]  
uPD78F0535AGBA [CX3011]  
uPD78F0535AGC [CX3013]  
uPD78F0535AGCA2 [CX3013]  
uPD78F0535AGKA [CX3012]  
uPD78F0535GB [CX3011]  
uPD78F0535GBA2 [CX3011]  
uPD78F0535GCA [CX3013]  
uPD78F0535GK [CX3012]  
uPD78F0535GKA2 [CX3012]  
uPD78F0536AGBA [CX3011]  
uPD78F0536AGC [CX3013]  
uPD78F0536AGCA2 [CX3013]  
uPD78F0536AGKA [CX3012]  
uPD78F0536GB [CX3011]  
uPD78F0536GBA2 [CX3011]  
uPD78F0536GCA [CX3013]  
uPD78F0536GK [CX3012]  
uPD78F0536GKA2 [CX3012]  
uPD78F0537ADGBA [CX3011]  
uPD78F0537ADGC [CX3013]  
uPD78F0537ADGCA2 [CX3013]  
uPD78F0537ADGKA [CX3012]  
uPD78F0537AGB [CX3011]  
uPD78F0537AGBA2 [CX3011]  
uPD78F0537AGCA [CX3013]  
uPD78F0537AGK [CX3012]  
uPD78F0537AGKA2 [CX3012]  
uPD78F0537DGBA [CX3011]  
uPD78F0537DGC [CX3013]  
uPD78F0537DGCA2 [CX3013]  
uPD78F0537DGKA [CX3012]  
uPD78F0537GB [CX3011]  
uPD78F0537GBA2 [CX3011]  
uPD78F0537GCA [CX3013]  
uPD78F0537GK [CX3012]  
uPD78F0537GKA2 [CX3012]  
uPD78F0544AGCA [CX3017]  
uPD78F0544AGK [CX3016]  
uPD78F0544AGKA2 [CX3016]  
uPD78F0544GCA [CX3017]  
uPD78F0544GK [CX3016]  
uPD78F0544GKA2 [CX3016]  
uPD78F0545AGCA [CX3017]  
uPD78F0545AGK [CX3016]  
uPD78F0545AGKA2 [CX3016]  
uPD78F0545GCA [CX3017]  
uPD78F0545GK [CX3016]  
uPD78F0545GKA2 [CX3016]  
uPD78F0546AGKA [CX3016]  
uPD78F0546GK [CX3016]  
uPD78F0546GKA2 [CX3016]  
uPD78F0547ADGCA [CX3017]  
uPD78F0547ADGK [CX3016]  
uPD78F0547ADGKA2 [CX3016]  
uPD78F0547AGCA [CX3017]  
uPD78F0547AGK [CX3016]

uPD78F0547AGKA [CX3016]  
uPD78F0547DGC [CX3017]  
uPD78F0547DGCA2 [CX3017]  
uPD78F0547DGKA [CX3016]  
uPD78F0547GC [CX3017]  
uPD78F0547GCA2 [CX3017]  
uPD78F0547GKA [CX3016]  
uPD78F0854MA [CX1001]  
uPD78F0856MA [CX1001]  
uPD78F0858MC [CX1027]  
uPD78F0864MC [CX1027]  
uPD78F1804AK8 [CX4015]  
uPD78F1804AK8A2 [CX4015]  
uPD78F1804AMCA [CX1027]  
uPD78F1804K8 [CX4015]  
uPD78F1804K8A2 [CX4015]  
uPD78F1804MCA [CX1027]  
uPD78F1805AK8 [CX4015]  
uPD78F1805AK8A2 [CX4015]  
uPD78F1805AMCA [CX1027]  
uPD78F1805K8 [CX4015]  
uPD78F1805K8A2 [CX4015]  
uPD78F1805MCA [CX1027]  
uPD78F1806AK8 [CX4015]  
uPD78F1806AK8A2 [CX4015]  
uPD78F1806AMCA [CX1027]  
uPD78F1806K8 [CX4015]  
uPD78F1806K8A2 [CX4015]  
uPD78F1806MCA [CX1027]  
uPD78F1807AK8 [CX4015]  
uPD78F1807AK8A2 [CX4015]  
uPD78F1807AMCA [CX1027]  
uPD78F1807K8 [CX4015]  
uPD78F1807K8A2 [CX4015]  
uPD78F1807MCA [CX1027]  
uPD78F1808AK8 [CX4017]  
uPD78F1808AK8A2 [CX4017]  
uPD78F1808K8A [CX4017]  
uPD78F1809AK8 [CX4017]  
uPD78F1809AK8A2 [CX4017]  
uPD78F1809K8A [CX4017]  
uPD78F1810AK8 [CX4017]  
uPD78F1810AK8A2 [CX4017]  
uPD78F1810K8A [CX4017]  
uPD78F1811AK8 [CX4017]  
uPD78F1811AK8A2 [CX4017]  
uPD78F1811K8A [CX4017]  
uPD78F1812AGA [CX3007]  
uPD78F1812AGAA2 [CX3007]  
uPD78F1812AK8A [CX3007]  
uPD78F1812GA [CX3007]  
uPD78F1812GAA2 [CX3007]  
uPD78F1812K8A [CX3007]  
uPD78F1813AGA [CX3007]  
uPD78F1813AGAA2 [CX3007]  
uPD78F1813AK8A [CX3007]  
uPD78F1813GA [CX3007]  
uPD78F1813GAA2 [CX3007]  
uPD78F1813K8A [CX3007]

uPD78F0547AGKA2 [CX3016]  
uPD78F0547DGCA [CX3017]  
uPD78F0547DGK [CX3016]  
uPD78F0547DGKA2 [CX3016]  
uPD78F0547GCA [CX3017]  
uPD78F0547GK [CX3016]  
uPD78F0547GKA2 [CX3016]  
uPD78F0855MA [CX1001]  
uPD78F0857MC [CX1027]  
uPD78F0859MC [CX1027]  
uPD78F0865MC [CX1027]  
uPD78F1804AK8A [CX4015]  
uPD78F1804AMC [CX1027]  
uPD78F1804AMCA2 [CX1027]  
uPD78F1804K8A [CX4015]  
uPD78F1804MC [CX1027]  
uPD78F1804MCA2 [CX1027]  
uPD78F1805AK8A [CX4015]  
uPD78F1805AMC [CX1027]  
uPD78F1805AMCA2 [CX1027]  
uPD78F1805K8A [CX4015]  
uPD78F1805MC [CX1027]  
uPD78F1805MCA2 [CX1027]  
uPD78F1806AK8A [CX4015]  
uPD78F1806AMC [CX1027]  
uPD78F1806AMCA2 [CX1027]  
uPD78F1806K8A [CX4015]  
uPD78F1806MC [CX1027]  
uPD78F1806MCA2 [CX1027]  
uPD78F1807AK8A [CX4015]  
uPD78F1807AMC [CX1027]  
uPD78F1807AMCA2 [CX1027]  
uPD78F1807K8A [CX4015]  
uPD78F1807MC [CX1027]  
uPD78F1807MCA2 [CX1027]  
uPD78F1808AK8A [CX4017]  
uPD78F1808K8 [CX4017]  
uPD78F1808K8A2 [CX4017]  
uPD78F1809AK8A [CX4017]  
uPD78F1809K8 [CX4017]  
uPD78F1809K8A2 [CX4017]  
uPD78F1810AK8A [CX4017]  
uPD78F1810K8 [CX4017]  
uPD78F1810K8A2 [CX4017]  
uPD78F1811AK8A [CX4017]  
uPD78F1811K8 [CX4017]  
uPD78F1811K8A2 [CX4017]  
uPD78F1812AGAA [CX3007]  
uPD78F1812AK8 [CX3007]  
uPD78F1812AK8A2 [CX3007]  
uPD78F1812GAA [CX3007]  
uPD78F1812K8 [CX3007]  
uPD78F1812K8A2 [CX3007]  
uPD78F1813AGAA [CX3007]  
uPD78F1813AK8 [CX3007]  
uPD78F1813AK8A2 [CX3007]  
uPD78F1813GAA [CX3007]  
uPD78F1813K8 [CX3007]  
uPD78F1813K8A2 [CX3007]

uPD78F1814AGA [CX3007]  
uPD78F1814AGAA2 [CX3007]  
uPD78F1814AK8A [CX3007]  
uPD78F1814GA [CX3007]  
uPD78F1814GAA2 [CX3007]  
uPD78F1814K8A [CX3007]  
uPD78F1815AGA [CX3007]  
uPD78F1815AGAA2 [CX3007]  
uPD78F1815AK8A [CX3007]  
uPD78F1815GA [CX3007]  
uPD78F1815GAA2 [CX3007]  
uPD78F1815K8A [CX3007]  
uPD78F1816AGA [CX3007]  
uPD78F1816AGAA2 [CX3007]  
uPD78F1816AK8A [CX3007]  
uPD78F1816GA [CX3007]  
uPD78F1816GAA2 [CX3007]  
uPD78F1816K8A [CX3007]  
uPD78F1817AGA [CX3007]  
uPD78F1817AGAA2 [CX3007]  
uPD78F1817AK8A [CX3007]  
uPD78F1817GA [CX3007]  
uPD78F1817GAA2 [CX3007]  
uPD78F1817K8A [CX3007]  
uPD78F1818AGB [CX3011]  
uPD78F1818AGBA2 [CX3011]  
uPD78F1818GBA [CX3011]  
uPD78F1819AGB [CX3011]  
uPD78F1819AGBA2 [CX3011]  
uPD78F1819GBA [CX3011]  
uPD78F1820AGB [CX3011]  
uPD78F1820AGBA2 [CX3011]  
uPD78F1820GBA [CX3011]  
uPD78F1821AGB [CX3011]  
uPD78F1821AGBA2 [CX3011]  
uPD78F1821GBA [CX3011]  
uPD78F1822AGB [CX3011]  
uPD78F1822AGBA2 [CX3011]  
uPD78F1822GBA [CX3011]  
uPD78F1823AGK [CX3016]  
uPD78F1823AGKA2 [CX3016]  
uPD78F1823GKA [CX3016]  
uPD78F1824AGK [CX3016]  
uPD78F1824AGKA2 [CX3016]  
uPD78F1824GKA [CX3016]  
uPD78F1825AGK [CX3016]  
uPD78F1825AGKA2 [CX3016]  
uPD78F1825GKA [CX3016]  
uPD78F1826AGA [CX3007]  
uPD78F1826AGAA2 [CX3007]  
uPD78F1826AK8A [CX3007]  
uPD78F1826GA [CX3007]  
uPD78F1826GAA2 [CX3007]  
uPD78F1826K8A [CX3007]  
uPD78F1827AGA [CX3007]  
uPD78F1827AGAA2 [CX3007]  
uPD78F1827AK8A [CX3007]  
uPD78F1827GA [CX3007]  
uPD78F1827GAA2 [CX3007]

uPD78F1814AGAA [CX3007]  
uPD78F1814AK8 [CX3007]  
uPD78F1814AK8A2 [CX3007]  
uPD78F1814GAA [CX3007]  
uPD78F1814K8 [CX3007]  
uPD78F1814K8A2 [CX3007]  
uPD78F1815AGAA [CX3007]  
uPD78F1815AK8 [CX3007]  
uPD78F1815AK8A2 [CX3007]  
uPD78F1815GAA [CX3007]  
uPD78F1815K8 [CX3007]  
uPD78F1815K8A2 [CX3007]  
uPD78F1816AGAA [CX3007]  
uPD78F1816AK8 [CX3007]  
uPD78F1816AK8A2 [CX3007]  
uPD78F1816GAA [CX3007]  
uPD78F1816K8 [CX3007]  
uPD78F1816K8A2 [CX3007]  
uPD78F1817AGAA [CX3007]  
uPD78F1817AK8 [CX3007]  
uPD78F1817AK8A2 [CX3007]  
uPD78F1817GAA [CX3007]  
uPD78F1817K8 [CX3007]  
uPD78F1817K8A2 [CX3007]  
uPD78F1818AGBA [CX3011]  
uPD78F1818GB [CX3011]  
uPD78F1818GBA2 [CX3011]  
uPD78F1819AGBA [CX3011]  
uPD78F1819GB [CX3011]  
uPD78F1819GBA2 [CX3011]  
uPD78F1820AGBA [CX3011]  
uPD78F1820GB [CX3011]  
uPD78F1820GBA2 [CX3011]  
uPD78F1821AGBA [CX3011]  
uPD78F1821GB [CX3011]  
uPD78F1821GBA2 [CX3011]  
uPD78F1822AGBA [CX3011]  
uPD78F1822GB [CX3011]  
uPD78F1822GBA2 [CX3011]  
uPD78F1823AGKA [CX3016]  
uPD78F1823GK [CX3016]  
uPD78F1823GKA2 [CX3016]  
uPD78F1824AGKA [CX3016]  
uPD78F1824GK [CX3016]  
uPD78F1824GKA2 [CX3016]  
uPD78F1825AGKA [CX3016]  
uPD78F1825GK [CX3016]  
uPD78F1825GKA2 [CX3016]  
uPD78F1826AGAA [CX3007]  
uPD78F1826AK8 [CX3007]  
uPD78F1826AK8A2 [CX3007]  
uPD78F1826GAA [CX3007]  
uPD78F1826K8 [CX3007]  
uPD78F1826K8A2 [CX3007]  
uPD78F1827AGAA [CX3007]  
uPD78F1827AK8 [CX3007]  
uPD78F1827AK8A2 [CX3007]  
uPD78F1827GAA [CX3007]  
uPD78F1827K8 [CX3007]

uPD78F1827K8A [CX3007]  
uPD78F1828AGA [CX3007]  
uPD78F1828AGAA2 [CX3007]  
uPD78F1828AK8A [CX3007]  
uPD78F1828GA [CX3007]  
uPD78F1828GAA2 [CX3007]  
uPD78F1828K8A [CX3007]  
uPD78F1829AGA [CX3007]  
uPD78F1829AGAA2 [CX3007]  
uPD78F1829AK8A [CX3007]  
uPD78F1829GA [CX3007]  
uPD78F1829GAA2 [CX3007]  
uPD78F1829K8A [CX3007]  
uPD78F1830AGA [CX3007]  
uPD78F1830AGAA2 [CX3007]  
uPD78F1830AK8A [CX3007]  
uPD78F1830GA [CX3007]  
uPD78F1830GAA2 [CX3007]  
uPD78F1830K8A [CX3007]  
uPD78F1831AGB [CX3011]  
uPD78F1831AGBA2 [CX3011]  
uPD78F1831GBA [CX3011]  
uPD78F1832AGB [CX3011]  
uPD78F1832AGBA2 [CX3011]  
uPD78F1832GBA [CX3011]  
uPD78F1833AGB [CX3011]  
uPD78F1833AGBA2 [CX3011]  
uPD78F1833GBA [CX3011]  
uPD78F1834AGB [CX3011]  
uPD78F1834AGBA2 [CX3011]  
uPD78F1834GBA [CX3011]  
uPD78F1835AGB [CX3011]  
uPD78F1835AGBA2 [CX3011]  
uPD78F1835GBA [CX3011]  
uPD78F1836AGK [CX3016]  
uPD78F1836AGKA2 [CX3016]  
uPD78F1836GKA [CX3016]  
uPD78F1837AGK [CX3016]  
uPD78F1837AGKA2 [CX3016]  
uPD78F1837GKA [CX3016]  
uPD78F1838AGK [CX3016]  
uPD78F1838AGKA2 [CX3016]  
uPD78F1838GKA [CX3016]  
uPD78F1839AGK [CX3016]  
uPD78F1839AGKA2 [CX3016]  
uPD78F1839GKA [CX3016]  
uPD78F1840AGK [CX3021]  
uPD78F1840AGKA2 [CX3021]  
uPD78F1840GKA [CX3021]  
uPD78F1841AGK [CX3021]  
uPD78F1841AGKA2 [CX3021]  
uPD78F1841GKA [CX3021]  
uPD78F1842AGK [CX3021]  
uPD78F1842AGKA2 [CX3021]  
uPD78F1842GKA [CX3021]  
uPD78F1843AGK [CX3021]  
uPD78F1843AGKA2 [CX3021]  
uPD78F1843GKA [CX3021]  
uPD78F1844AGK [CX3021]

uPD78F1827K8A2 [CX3007]  
uPD78F1828AGAA [CX3007]  
uPD78F1828AK8 [CX3007]  
uPD78F1828AK8A2 [CX3007]  
uPD78F1828GAA [CX3007]  
uPD78F1828K8 [CX3007]  
uPD78F1828K8A2 [CX3007]  
uPD78F1829AGAA [CX3007]  
uPD78F1829AK8 [CX3007]  
uPD78F1829AK8A2 [CX3007]  
uPD78F1829GAA [CX3007]  
uPD78F1829K8 [CX3007]  
uPD78F1829K8A2 [CX3007]  
uPD78F1830AGAA [CX3007]  
uPD78F1830AK8 [CX3007]  
uPD78F1830AK8A2 [CX3007]  
uPD78F1830GAA [CX3007]  
uPD78F1830K8 [CX3007]  
uPD78F1830K8A2 [CX3007]  
uPD78F1831AGBA [CX3011]  
uPD78F1831GB [CX3011]  
uPD78F1831GBA2 [CX3011]  
uPD78F1832AGBA [CX3011]  
uPD78F1832GB [CX3011]  
uPD78F1832GBA2 [CX3011]  
uPD78F1833AGBA [CX3011]  
uPD78F1833GB [CX3011]  
uPD78F1833GBA2 [CX3011]  
uPD78F1834AGBA [CX3011]  
uPD78F1834GB [CX3011]  
uPD78F1834GBA2 [CX3011]  
uPD78F1835AGBA [CX3011]  
uPD78F1835GB [CX3011]  
uPD78F1835GBA2 [CX3011]  
uPD78F1836AGKA [CX3016]  
uPD78F1836GK [CX3016]  
uPD78F1836GKA2 [CX3016]  
uPD78F1837AGKA [CX3016]  
uPD78F1837GK [CX3016]  
uPD78F1837GKA2 [CX3016]  
uPD78F1838AGKA [CX3016]  
uPD78F1838GK [CX3016]  
uPD78F1838GKA2 [CX3016]  
uPD78F1839AGKA [CX3016]  
uPD78F1839GK [CX3016]  
uPD78F1839GKA2 [CX3016]  
uPD78F1840AGKA [CX3021]  
uPD78F1840GK [CX3021]  
uPD78F1840GKA2 [CX3021]  
uPD78F1841AGKA [CX3021]  
uPD78F1841GK [CX3021]  
uPD78F1841GKA2 [CX3021]  
uPD78F1842AGKA [CX3021]  
uPD78F1842GK [CX3021]  
uPD78F1842GKA2 [CX3021]  
uPD78F1843AGKA [CX3021]  
uPD78F1843GK [CX3021]  
uPD78F1843GKA2 [CX3021]  
uPD78F1844AGKA [CX3021]

uPD78F1844AGKA2 [CX3021]  
uPD78F1844GKA [CX3021]  
uPD78F1845AGK [CX3021]  
uPD78F1845AGKA2 [CX3021]  
uPD78F1845GKA [CX3021]  
uPD78F9025@SDIP42 [CX0042]  
uPD78F9025A@SDIP42 [CX0042]  
uPD78F9025B@SDIP42 [CX0042]  
uPD78F9026@SDIP42 [CX0042]  
uPD78F9026A@SDIP42 [CX0042]  
uPD78F9026B@SDIP42 [CX0042]  
uPD78F9045@SDIP42 [CX0042]  
uPD78F9045A@SDIP42 [CX0042]  
uPD78F9045B@SDIP42 [CX0042]  
uPD78F9046@SDIP42 [CX0042]  
uPD78F9046A@SDIP42 [CX0042]  
uPD78F9046B@SDIP42 [CX0042]  
uPD79F7020GB [CX3010]  
UPD79F7024MC [CX1074]  
UPD79F7026@QFP32 [CX3001]

uPD78F1844GK [CX3021]  
uPD78F1844GKA2 [CX3021]  
uPD78F1845AGKA [CX3021]  
uPD78F1845GK [CX3021]  
uPD78F1845GKA2 [CX3021]  
uPD78F9025@TQFP44 [CX3002]  
uPD78F9025A@TQFP44 [CX3002]  
uPD78F9025B@TQFP44 [CX3002]  
uPD78F9026@TQFP44 [CX3002]  
uPD78F9026A@TQFP44 [CX3002]  
uPD78F9026B@TQFP44 [CX3002]  
uPD78F9045@TQFP44 [CX3002]  
uPD78F9045A@TQFP44 [CX3002]  
uPD78F9045B@TQFP44 [CX3002]  
uPD78F9046@TQFP44 [CX3002]  
uPD78F9046A@TQFP44 [CX3002]  
uPD78F9046B@TQFP44 [CX3002]  
UPD79F7023MC [CX1074]  
UPD79F7025@QFP32 [CX3001]

## RICHTEK

### E (E) PROM/FRAM/NVRAM

RT6729@QFN28 [CX4036]

### MICROCONTROLLER

CM601@QFN24 [CX4012]  
RT6505@QFN28 [CX4036]  
RT6716@WLCSP48 [CX5238]  
RT6914@QFN40(left down) [CX4017]

CM602@QFN28 [CX4013]  
RT6505@QFN28(left down) [CX4036]  
RT6914@QFN40 [CX4017]

## RICOH

### E (E) PROM/FRAM/NVRAM

RD27C256 [CX0001]  
RD27C64 [CX0001]

RD27C32 [CX0001]

## ROCKWELL

### E (E) PROM/FRAM/NVRAM

R2764 [CX0001]  
R2764P [CX0001]  
R2816 [CX0001]  
R52B13 [CX0001]

R2764C [CX0001]  
R27C64 [CX0001]  
R5213 [CX0001]  
R52B33 [CX0001]

## ROHM

### E (E) PROM/FRAM/NVRAM

BH9020 [CX1045]  
BR24A01A(FJ) [CX1079]  
BR24A02(FJ) [CX1079]  
BR24A04(FJ) [CX1079]  
BR24A08(FJ) [CX1079]  
BR24A16(FJ) [CX1079]  
BR24A32(FJ) [CX1045]  
BR24A64(FJ) [CX1045]  
BR24C01@TSSOP8 [CX1059]  
BR24C01A [CX0001]  
BR24C01A(FJ) [CX1079]  
BR24C02 [CX0001]  
BR24C02(FJ) [CX1079]  
BR24C02@SOP8 [CX1079]  
BR24C02@TSSOP8(3\*3mm) [CX1015]  
BR24C04(F) [CX1079]  
BR24C04(FV) [CX1059]  
BR24C04@TSSOP8 [CX1059]  
BR24C08 [CX0001]  
BR24C08(FJ) [CX1079]  
BR24C08@SOP8 [CX1079]  
BR24C08@TSSOP8(3\*3mm) [CX1015]  
BR24C16(F) [CX1079]  
BR24C16(FV) [CX1059]  
BR24C21(F) [CX1079]  
BR24C21(FV) [CX1059]  
BR24C32(F) [CX1045]  
BR24C64(F) [CX1045]  
BR24E16(F) [CX1079]  
BR24E16(FV) [CX1059]  
BR24G01(F) [CX1079]  
BR24G01(FV) [CX1059]  
BR24G02(F) [CX1079]  
BR24G02(FV) [CX1059]  
BR24G04(F) [CX1079]  
BR24G04(FV) [CX1059]  
BR24G08(FJ) [CX1079]  
BR24G08(FVJ) [CX1059]  
BR24G08(FVT) [CX1059]  
BR24G128(F) [CX1045]  
BR24G128(FV) [CX1059]  
BR24G16 [CX0001]  
BR24G16(FJ) [CX1079]  
BR24G16(FVM) [CX1015]  
BR24G256(F) [CX1045]  
BR24G256(FV) [CX1059]  
BR24G32 [CX0001]  
BR24G32(FJ) [CX1045]  
BR24G32(FVT) [CX1059]  
BR24G64(F) [CX1045]  
BR24G64(FV) [CX1059]  
BR24L01A [CX0001]  
BR24L01A(FJ) [CX1079]  
BR24L01A(FVM) [CX1015]  
BR24L02 [CX0001]  
BR24L02(FJ) [CX1079]  
BR24L02(FVM) [CX1015]  
BR24L04 [CX0001]  
BR24L04(FJ) [CX1079]  
BR24A01A(F) [CX1079]  
BR24A02(F) [CX1079]  
BR24A04(F) [CX1079]  
BR24A08(F) [CX1079]  
BR24A16(F) [CX1079]  
BR24A32(F) [CX1045]  
BR24A64(F) [CX1045]  
BR24C01@SOP8 [CX1079]  
BR24C01@TSSOP8(3\*3mm) [CX1015]  
BR24C01A(F) [CX1079]  
BR24C01A(FV) [CX1059]  
BR24C02(F) [CX1079]  
BR24C02(FV) [CX1059]  
BR24C02@TSSOP8 [CX1059]  
BR24C04 [CX0001]  
BR24C04(FJ) [CX1079]  
BR24C04@SOP8 [CX1079]  
BR24C04@TSSOP8(3\*3mm) [CX1015]  
BR24C08(F) [CX1079]  
BR24C08(FV) [CX1059]  
BR24C08@TSSOP8 [CX1059]  
BR24C16 [CX0001]  
BR24C16(FJ) [CX1079]  
BR24C21 [CX0001]  
BR24C21(FJ) [CX1079]  
BR24C32 [CX0001]  
BR24C64 [CX0001]  
BR24E16 [CX0001]  
BR24E16(FJ) [CX1079]  
BR24G01 [CX0001]  
BR24G01(FJ) [CX1079]  
BR24G02 [CX0001]  
BR24G02(FJ) [CX1079]  
BR24G04 [CX0001]  
BR24G04(FJ) [CX1079]  
BR24G08(F) [CX1079]  
BR24G08(FV) [CX1059]  
BR24G08(FVM) [CX1015]  
BR24G128 [CX0001]  
BR24G128(FJ) [CX1045]  
BR24G128(FVT) [CX1059]  
BR24G16(F) [CX1079]  
BR24G16(FV) [CX1059]  
BR24G256 [CX0001]  
BR24G256(FJ) [CX1045]  
BR24G256(FVT) [CX1059]  
BR24G32(F) [CX1045]  
BR24G32(FV) [CX1059]  
BR24G64 [CX0001]  
BR24G64(FJ) [CX1045]  
BR24G64(FVT) [CX1059]  
BR24L01A(F) [CX1079]  
BR24L01A(FV) [CX1059]  
BR24L01A@VSON8 [CX4002]  
BR24L02(F) [CX1079]  
BR24L02(FV) [CX1059]  
BR24L02@VSON8 [CX4002]  
BR24L04(F) [CX1079]  
BR24L04(FV) [CX1059]

BR24L04(FVM) [CX1015]  
BR24L08 [CX0001]  
BR24L08(FJ) [CX1079]  
BR24L08(FVM) [CX1015]  
BR24L16 [CX0001]  
BR24L16(FJ) [CX1079]  
BR24L16(FVM) [CX1015]  
BR24L32(F) [CX1045]  
BR24L32(FV) [CX1059]  
BR24L64(F) [CX1045]  
BR24L64(FV) [CX1059]  
BR24S08(FJ) [CX1079]  
BR24S08(FVJ) [CX1059]  
BR24S08(FVT) [CX1059]  
BR24S128(F) [CX1045]  
BR24S128(FV) [CX1059]  
BR24S16(F) [CX1079]  
BR24S16(FV) [CX1059]  
BR24S256 [CX0001]  
BR24S256(FJ) [CX1045]  
BR24S32 [CX0001]  
BR24S32(FJ) [CX1045]  
BR24S64 [CX0001]  
BR24S64(FJ) [CX1045]  
BR24T01 [CX0001]  
BR24T01(FJ) [CX1079]  
BR24T02 [CX0001]  
BR24T02(FJ) [CX1079]  
BR24T02@VSON8 [CX4047]  
BR24T04(F) [CX1079]  
BR24T04(FV) [CX1059]  
BR24T08(FJ) [CX1079]  
BR24T08(FVJ) [CX1059]  
BR24T08(FVT) [CX1059]  
BR24T128(F) [CX1045]  
BR24T128(FV) [CX1059]  
BR24T16 [CX0001]  
BR24T16(FJ) [CX1045]  
BR24T16(FVM) [CX1015]  
BR24T1M [CX0001]  
BR24T256 [CX0001]  
BR24T256(FJ) [CX1045]  
BR24T256(FVT) [CX1059]  
BR24T32(F) [CX1045]  
BR24T32(FV) [CX1059]  
BR24T32@VSON8 [CX4047]  
BR24T512(F) [CX1045]  
BR24T512(FV) [CX1059]  
BR24T64 [CX0001]  
BR24T64(FJ) [CX1045]  
BR24T64(FVT) [CX1059]  
BR25010@TSSOP8 [CX1059]  
BR25020@TSSOP8 [CX1059]  
BR25040@TSSOP8 [CX1059]  
BR25080@TSSOP8 [CX1059]  
BR25160@TSSOP8 [CX1059]  
BR25H010(F) [CX1045]  
BR25H020(F) [CX1045]  
BR25H040(F) [CX1045]  
BR24L04@VSON8 [CX4002]  
BR24L08(F) [CX1079]  
BR24L08(FV) [CX1059]  
BR24L08@VSON8 [CX4002]  
BR24L16(F) [CX1079]  
BR24L16(FV) [CX1059]  
BR24L32 [CX0001]  
BR24L32(FJ) [CX1045]  
BR24L64 [CX0001]  
BR24L64(FJ) [CX1045]  
BR24S08(F) [CX1079]  
BR24S08(FV) [CX1059]  
BR24S08(FVM) [CX1015]  
BR24S128 [CX0001]  
BR24S128(FJ) [CX1045]  
BR24S16 [CX0001]  
BR24S16(FJ) [CX1079]  
BR24S16(FVM) [CX1015]  
BR24S256(F) [CX1045]  
BR24S256(FV) [CX1059]  
BR24S32(F) [CX1045]  
BR24S32(FV) [CX1059]  
BR24S64(F) [CX1045]  
BR24S64(FV) [CX1059]  
BR24T01(F) [CX1079]  
BR24T01(FV) [CX1059]  
BR24T02(F) [CX1079]  
BR24T02(FV) [CX1059]  
BR24T04 [CX0001]  
BR24T04(FJ) [CX1079]  
BR24T08(F) [CX1079]  
BR24T08(FV) [CX1059]  
BR24T08(FVM) [CX1015]  
BR24T128 [CX0001]  
BR24T128(FJ) [CX1045]  
BR24T128(FVT) [CX1059]  
BR24T16(F) [CX1079]  
BR24T16(FV) [CX1059]  
BR24T16@VSON8 [CX4047]  
BR24T1MF [CX1044]  
BR24T256(F) [CX1045]  
BR24T256(FV) [CX1059]  
BR24T32 [CX0001]  
BR24T32(FJ) [CX1045]  
BR24T32(FVT) [CX1059]  
BR24T512 [CX0001]  
BR24T512(FJ) [CX1045]  
BR24T512(FVT) [CX1059]  
BR24T64(F) [CX1045]  
BR24T64(FV) [CX1059]  
BR25010@SOIC8 [CX1045]  
BR25020@SOIC8 [CX1045]  
BR25040@SOIC8 [CX1045]  
BR25080@SOIC8 [CX1045]  
BR25160@SOIC8 [CX1045]  
BR25320@SOIC8 [CX1045]  
BR25H010(FJ) [CX1045]  
BR25H020(FJ) [CX1045]  
BR25H040(FJ) [CX1045]

BR25H080(F) [CX1045]  
BR25H080(FVT) [CX1059]  
BR25H160(FJ) [CX1045]  
BR25H320(F) [CX1045]  
BR25H320(FVT) [CX1059]  
BR25L010(F) [CX1045]  
BR25L010(FV) [CX1059]  
BR25L020 [CX0001]  
BR25L020(FJ) [CX1045]  
BR25L020(FVM) [CX1015]  
BR25L040(F) [CX1045]  
BR25L040(FV) [CX1059]  
BR25L080 [CX0001]  
BR25L080(FJ) [CX1045]  
BR25L160 [CX0001]  
BR25L160(FJ) [CX1045]  
BR25L320 [CX0001]  
BR25L320(FJ) [CX1045]  
BR25L640 [CX0001]  
BR25L640(FJ) [CX1045]  
BR25S128F [CX1079]  
BR25S128FV [CX1059]  
BR25S256F [CX1079]  
BR25S320F [CX1079]  
BR25S320FV [CX1059]  
BR25S320FVM [CX1015]  
BR25S320NUX [CX4002]  
BR25S640FJ [CX1045]  
BR25S640FVJ [CX1015]  
BR25S640FVT [CX1059]  
BR34L02 [CX0001]  
BR34L02(FJ) [CX1045]  
BR34L02(FVM) [CX1015]  
BR35H010FJ [CX1045]  
BR35H020FJ [CX1045]  
BR35H040FJ [CX1045]  
BR35H080FJ [CX1045]  
BR35H128F [CX1079]  
BR35H160F [CX1079]  
BR35H160FVM [CX1015]  
BR35H320F [CX1079]  
BR35H320FVM [CX1015]  
BR35H640F [CX1079]  
BR35H640FVT [CX1059]  
BR9010(F) [CX1045]  
BR9010(RFV) [CX1059]  
BR9016 [CX0001]  
BR9016(RFV) [CX1059]  
BR9016A(RFV) [CX1059]  
BR9020 [CX0001]  
BR9020(FV) [CX1059]  
BR9020(RFVM) [CX1015]  
BR9040(F) [CX1045]  
BR9040(RFV) [CX1059]  
BR9080 [CX0001]  
BR9080(RFV) [CX1059]  
BR9080A(F) [CX1045]  
BR9080A(RFV) [CX1059]  
BR93A46(F) [CX1045]

BR25H080(FJ) [CX1045]  
BR25H160(F) [CX1045]  
BR25H160(FVT) [CX1059]  
BR25H320(FJ) [CX1045]  
BR25L010 [CX0001]  
BR25L010(FJ) [CX1045]  
BR25L010(FVM) [CX1015]  
BR25L020(F) [CX1045]  
BR25L020(FV) [CX1059]  
BR25L040 [CX0001]  
BR25L040(FJ) [CX1045]  
BR25L040(FVM) [CX1015]  
BR25L080(F) [CX1045]  
BR25L080(FV) [CX1059]  
BR25L160(F) [CX1045]  
BR25L160(FV) [CX1059]  
BR25L320(F) [CX1045]  
BR25L320(FV) [CX1059]  
BR25L640(F) [CX1045]  
BR25L640(FV) [CX1059]  
BR25S128FJ [CX1045]  
BR25S128FVT [CX1059]  
BR25S256FJ [CX1045]  
BR25S320FJ [CX1045]  
BR25S320FVJ [CX1015]  
BR25S320FVT [CX1059]  
BR25S640F [CX1079]  
BR25S640FV [CX1059]  
BR25S640FVM [CX1015]  
BR34C02A [CX1059]  
BR34L02(F) [CX1045]  
BR34L02(FV) [CX1059]  
BR35H010F [CX1079]  
BR35H020F [CX1079]  
BR35H040F [CX1079]  
BR35H080F [CX1079]  
BR35H080FVT [CX1059]  
BR35H128FJ [CX1045]  
BR35H160FJ [CX1045]  
BR35H160FVT [CX1059]  
BR35H320FJ [CX1045]  
BR35H320FVT [CX1059]  
BR35H640FJ [CX1045]  
BR9010 [CX0001]  
BR9010(FV) [CX1059]  
BR9010(RFVM) [CX1015]  
BR9016(F) [CX1045]  
BR9016A(F) [CX1045]  
BR9016A(RFVM) [CX1015]  
BR9020(F) [CX1045]  
BR9020(RFV) [CX1059]  
BR9040 [CX0001]  
BR9040(FV) [CX1059]  
BR9040(RFVM) [CX1015]  
BR9080(F) [CX1045]  
BR9080A [CX0001]  
BR9080A(FV) [CX1059]  
BR9080A(RFVM) [CX1015]  
BR93A46(FJ) [CX1045]



BR93A46(RF) [CX1045]  
BR93A56(F) [CX1045]  
BR93A56(RF) [CX1045]  
BR93A66(F) [CX1045]  
BR93A66(RF) [CX1045]  
BR93A76(F) [CX1045]  
BR93A76(RF) [CX1045]  
BR93A86(F) [CX1045]  
BR93A86(RF) [CX1045]  
BR93C46 [CX0001]  
BR93C46(FJ) [CX1045]  
BR93C46(RF) [CX1045]  
BR93C56 [CX0001]  
BR93C56(FJ) [CX1045]  
BR93C56(RF) [CX1045]  
BR93C66 [CX0001]  
BR93C66(FJ) [CX1045]  
BR93C66(RF) [CX1045]  
BR93H46(RF) [CX1044]  
BR93H56(RF) [CX1044]  
BR93H66(RF) [CX1044]  
BR93H76(RF) [CX1044]  
BR93H86(RF) [CX1044]  
BR93L46 [CX0001]  
BR93L46(FJ) [CX1045]  
BR93L46(RF) [CX1045]  
BR93L56 [CX0001]  
BR93L56(FJ) [CX1045]  
BR93L56(RF) [CX1045]  
BR93L66 [CX0001]  
BR93L66(FJ) [CX1045]  
BR93L66(RF) [CX1045]  
BR93L76(F) [CX1045]  
BR93L76(RF) [CX1045]  
BR93L76(RFV) [CX1059]  
BR93L76(RFVM) [CX1015]  
BR93L86(F) [CX1045]  
BR93L86(RF) [CX1045]  
BR93L86(RFV) [CX1059]  
BR93L86(RFVM) [CX1015]  
BR93LC46 [CX0001]  
BR93LC46(FJ) [CX1045]  
BR93LC46(RF) [CX1045]  
BR93LC56 [CX0001]  
BR93LC56(FJ) [CX1045]  
BR93LC56(RF) [CX1045]  
BR93LC66 [CX0001]  
BR93LC66(FJ) [CX1045]  
BR93LC66(RF) [CX1045]  
BR93LL46(F) [CX1045]  
BR95010@SOP8 [CX1045]  
BR95010@TSSOP8(3\*3) [CX1015]  
BR95020@TSSOP8 [CX1059]  
BR95040@SOP8 [CX1045]  
BR95040@TSSOP8(3\*3) [CX1015]  
BR95080@TSSOP8 [CX1059]  
BR95160@TSSOP8 [CX1059]  
BRCA016GWZ-W [CX0001]  
BU9832GUL-W [CX0001]

BR93A46(RFJ) [CX1045]  
BR93A56(FJ) [CX1045]  
BR93A56(RFJ) [CX1045]  
BR93A66(FJ) [CX1045]  
BR93A66(RFJ) [CX1045]  
BR93A76(FJ) [CX1045]  
BR93A76(RFJ) [CX1045]  
BR93A86(FJ) [CX1045]  
BR93A86(RFJ) [CX1045]  
BR93C46(F) [CX1045]  
BR93C46(FV) [CX1059]  
BR93C46(RFJ) [CX1045]  
BR93C56(F) [CX1045]  
BR93C56(FV) [CX1059]  
BR93C56(RFJ) [CX1045]  
BR93C66(F) [CX1045]  
BR93C66(FV) [CX1059]  
BR93C66(RFJ) [CX1045]  
BR93H46(RFJ) [CX1044]  
BR93H56(RFJ) [CX1044]  
BR93H66(RFJ) [CX1044]  
BR93H76(RFJ) [CX1044]  
BR93H86(RFJ) [CX1044]  
BR93L46(F) [CX1045]  
BR93L46(FV) [CX1059]  
BR93L46(RFJ) [CX1045]  
BR93L56(F) [CX1045]  
BR93L56(FV) [CX1059]  
BR93L56(RFJ) [CX1045]  
BR93L66(F) [CX1045]  
BR93L66(FV) [CX1059]  
BR93L66(RFJ) [CX1045]  
BR93L76(FJ) [CX1045]  
BR93L76(RFJ) [CX1045]  
BR93L76(RFVJ) [CX1015]  
BR93L76(RFVT) [CX1059]  
BR93L86(FJ) [CX1045]  
BR93L86(RFJ) [CX1045]  
BR93L86(RFVJ) [CX1015]  
BR93L86(RFVT) [CX1059]  
BR93LC46(F) [CX1045]  
BR93LC46(FV) [CX1059]  
BR93LC46(RFJ) [CX1045]  
BR93LC56(F) [CX1045]  
BR93LC56(FV) [CX1059]  
BR93LC56(RFJ) [CX1045]  
BR93LC66(F) [CX1045]  
BR93LC66(FV) [CX1059]  
BR93LC66(RFJ) [CX1045]  
BR93LL46(FV) [CX1059]  
BR95010@TSSOP8 [CX1059]  
BR95020@SOP8 [CX1045]  
BR95020@TSSOP8(3\*3) [CX1015]  
BR95040@TSSOP8 [CX1059]  
BR95080@SOP8 [CX1045]  
BR95160@SOP8 [CX1045]  
BR9877FV [CX1059]  
BU9829GUL-W [CX0001]  
BU9833GUL-W [CX0001]

BU9844GUL-W [CX0001]  
BU9880GUL-W [CX0001]  
BU9889GUL-W [CX0001]  
BU9891GUL-W [CX0001]  
BU99901GUZ-W [CX0001]

BU9847GUL-W [CX0001]  
BU9888FV-W [CX1059]  
BU9890GUL-W [CX0001]  
BU9897GUL-W [CX0001]

## SAIFUN

### E (E) PROM/FRAM/NVRAM

SA24C1024 [CX0001]  
SA24C512 [CX0001]  
SA24C512@TSSOP8 [CX1059]  
SA25C020@MLF8 [CX4005#1]  
SA25C040 [CX0001]  
SA25C040@SOIC8 [CX1045#1]  
SA25C080@MLF8 [CX4005#1]  
SA25C1024(H) [CX0001]  
SA25C1024(H)@SOIC8 [CX1045]  
SA25C1024(L)@CSP8 [CX4005]  
SA25C512(H)  
SA25C512(H)@SOIC8 [CX1045]  
SA25C512(L)@CSP8 [CX4005]  
SA25F005 [CX0001]  
SA25F005@SOIC8 [CX1045]  
SA25F010@MLF8 [CX4005]  
SA25F020 [CX0001]  
SA25F020@SOIC8 [CX1045#1]  
SA25F040@MLF8 [CX4005#1]  
SA25F080 [CX0001]  
SA25F080@SOIC8 [CX1045#1]  
SA25F160(ISP) [CX0001]  
SA25F160@MLF8(ISP) [CX0001]  
SA25F160@SOIC16(ISP) [CX0001]

SA24C1024@SOIC8 [CX1045]  
SA24C512@SOIC8 [CX1045]  
SA25C020 [CX0001]  
SA25C020@SOIC8 [CX1045#1]  
SA25C040@MLF8 [CX4005#1]  
SA25C080 [CX0001]  
SA25C080@SOIC8 [CX1045#1]  
SA25C1024(H)@CSP8 [CX4005]  
SA25C1024(L) [CX0001]  
SA25C1024(L)@SOIC8 [CX1045]  
SA25C512(H)@CSP8 [CX4005]  
SA25C512(L) [CX0001]  
SA25C512(L)@SOIC8 [CX1045]  
SA25F005@MLF8 [CX4005]  
SA25F010 [CX0001]  
SA25F010@SOIC8 [CX1045]  
SA25F020@MLF8 [CX4005#1]  
SA25F040 [CX0001]  
SA25F040@SOIC8 [CX1045#1]  
SA25F080@MLF8 [CX4005#1]  
SA25F160 [CX0001]  
SA25F160@MLF8 [CX4005#1]  
SA25F160@SOIC16 [CX1030]

## SAMSUNG

### E (E) PROM/FRAM/NVRAM

K5A3240CBM@FBGA69 [CX5001]  
K5A3240YBB@FBGA69 [CX5001]  
K5A3240YBM@FBGA69 [CX5001]  
K5A3240YTC@FBGA69 [CX5001]  
K5A3280YBA@FBGA69 [CX5001]  
K5A3280YBC@FBGA69 [CX5001]  
K5A3280YTA@FBGA69 [CX5001]  
K5A3280YTC@FBGA69 [CX5001]  
K5A3281CBM@FBGA69 [CX5001]  
K5A3340YBB@FBGA69 [CX5001]  
K5A3340YTB@FBGA69 [CX5001]  
K5A3380YBB@FBGA69 [CX5001]  
K5A3380YTB@FBGA69 [CX5001]  
K5A6317CBM@FBGA69 [CX5001]  
K5J6316CBM@FBGA69 [CX5001]  
K5J6332CBM@FBGA69 [CX5001]  
K5L2731CAA@FBGA64 [CX5001]  
K5L2763CAA@FBGA64 [CX5001]

K5A3240CTM@FBGA69 [CX5001]  
K5A3240YBC@FBGA69 [CX5001]  
K5A3240YTB@FBGA69 [CX5001]  
K5A3240YTM@FBGA69 [CX5001]  
K5A3280YBB@FBGA69 [CX5001]  
K5A3280YBM@FBGA69 [CX5001]  
K5A3280YTB@FBGA69 [CX5001]  
K5A3280YTM@FBGA69 [CX5001]  
K5A3281CTM@FBGA69 [CX5001]  
K5A3340YBC@FBGA69 [CX5001]  
K5A3340YTC@FBGA69 [CX5001]  
K5A3380YBC@FBGA69 [CX5001]  
K5A3380YTC@FBGA69 [CX5001]  
K5A6317CTM@FBGA69 [CX5001]  
K5J6316CTM@FBGA69 [CX5001]  
K5J6332CTM@FBGA69 [CX5001]  
K5L2731CAM@FBGA64 [CX5001]  
K5L2763CAM@FBGA64 [CX5001]

K5L2833ABA@FBGA84 [CX5001]	K5L2833ABM@FBGA84 [CX5001]
K5L2833ATA@FBGA84 [CX5001]	K5L2833ATA@FBGA84 (MW) [CX5005]
K5L2833ATM@FBGA84 [CX5001]	K5L2866ABA@FBGA84 [CX5001]
K5L2866ABB@FBGA84 [CX5001]	K5L2866ABC@FBGA84 [CX5001]
K5L2866ABD@FBGA84 [CX5001]	K5L2866ATA@FBGA84 [CX5001]
K5L2866ATB@FBGA84 [CX5001]	K5L2866ATC@FBGA84 [CX5001]
K5L2866ATD@FBGA84 [CX5001]	K5L2931CAM@FBGA64 [CX5001]
K5L3216CAM@FBGA69 [CX5001]	K5L3316CAM@FBGA69 [CX5001]
K5L5563CAA@FBGA84 [CX5001]	K5L5666ABA@FBGA84 [CX5001]
K5L5666ABB@FBGA84 [CX5001]	K5L5666ATA@FBGA84 [CX5001]
K5L5666ATB@FBGA84 [CX5001]	K5L6331CAA@FBGA56 [CX5045]
K5L6331CAA@FBGA56 (XW) [CX5005]	K5L6331CAM@FBGA56 [CX5045]
K5L6363CAM@FBGA56 [CX5045]	K5L6531CAM@FBGA56 [CX5045]
K5L6563CAM@FBGA56 [CX5045]	K5L6631CAA@FBGA56 [CX5045]
K5N2833ABB@FBGA56 [CX5135]	K5N2833ABM@FBGA56 [CX5066]
K5N2833ABM@FBGA56 (ZTE) [CX5183]	K5N2833ABM@FBGA84 [CX5001]
K5N2833ATB@FBGA56 [CX5135]	K5N2833ATM@FBGA56 [CX5066]
K5N2833ATM@FBGA56 (ZTE) [CX5183]	K5N2833ATM@FBGA84 [CX5001]
K5N2866ABB@FBGA56 [CX5135]	K5N2866ABD@FBGA56 [CX5135]
K5N2866ABE@FBGA56 [CX5135]	K5N2866ABM@FBGA56 [CX5066]
K5N2866ATB@FBGA56 [CX5135]	K5N2866ATD@FBGA56 [CX5135]
K5N2866ATE@FBGA56 [CX5135]	K5N2866ATF@FBGA56 [CX5135]
K5N2866ATM@FBGA56 [CX5066]	K5N3217ABA@FBGA56 [CX5135]
K5N3217ABM@FBGA56 [CX5066]	K5N3217ATA@FBGA56 [CX5135]
K5N3217ATM@FBGA56 [CX5066]	K5N5629ABA@FBGA56 [CX5066]
K5N5629ABA@FBGA56 (ZTE) [CX5183]	K5N5629ABB@FBGA56 [CX5066]
K5N5629ABC@FBGA56 [CX5066]	K5N5629ABM@FBGA56 [CX5066]
K5N5629ATA@FBGA56 [CX5066]	K5N5629ATA@FBGA56 (ZTE) [CX5183]
K5N5629ATB@FBGA56 [CX5066]	K5N5629ATC@FBGA56 [CX5066]
K5N5629ATM@FBGA56 [CX5066]	K5N5666ABB@FBGA56 [CX5066]
K5N5666ABB@FBGA56 (ZTE) [CX5183]	K5N5666ABD@FBGA56 [CX5066]
K5N5666ATB@FBGA56 [CX5066]	K5N5666ATB@FBGA56 (ZTE) [CX5183]
K5N5666ATD@FBGA56 [CX5066]	K5N6433ABB@FBGA52 [CX5135]
K5N6433ABM@FBGA52 [CX5135]	K5N6433ATB@FBGA52 [CX5135]
K5N6433ATM@FBGA52 [CX5135]	K8D1616UBA@TSOP48 [CX1004]
K8D1616UTA@TSOP48 [CX1004]	K8D1716UBA@TSOP48 [CX1004]
K8D1716UBC@FBGA48 [CX5039]	K8D1716UBC@TSOP48 [CX1004]
K8D1716UTA@TSOP48 [CX1004]	K8D1716UTC@FBGA48 [CX5039]
K8D1716UTC@TSOP48 [CX1004]	K8D3216UBB@FBGA48 [CX5039]
K8D3216UBB@TSOP48 [CX1004]	K8D3216UBC@FBGA48 [CX5039]
K8D3216UBC@TSOP48 [CX1004]	K8D3216UBM@TSOP48 [CX1004]
K8D3216UTB@FBGA48 [CX5039]	K8D3216UTB@TSOP48 [CX1004]
K8D3216UTC@FBGA48 [CX5039]	K8D3216UTC@TSOP48 [CX1004]
K8D3216UTM@TSOP48 [CX1004]	K8D3216UTM@TSOP48 (new) [CX1004]
K8D3316UBC@FBGA48 [CX5039]	K8D3316UBC@TSOP48 [CX1004]
K8D3316UBM@TSOP48 [CX1004]	K8D3316UTC@FBGA48 [CX5039]
K8D3316UTC@TSOP48 [CX1004]	K8D3316UTM@TSOP48 [CX1004]
K8D6316UBM@FBGA48 [CX5039]	K8D6316UBM@TSOP48 [CX1004]
K8D6316UTM@FBGA48 [CX5039]	K8D6316UTM@TSOP48 [CX1004]
K8D6416UM@SSOP56 [CX0051]	K8P2815UQB@FBGA64 [CX5074]
K8P2815UQB@FBGA80 [CX5001]	K8P2815UQC@FBGA80 [CX5001]
K8P3215UQB@FBGA48 [CX5002]	K8P3215UQB@FBGA64 [CX5074]
K8P3215UQB@TSOP48 [CX1004]	K8P5516UZB@FBGA64 [CX5074]
K8P5516UZB@TSOP56 [CX1011]	K8P5615UQA@FBGA83 [CX5001]
K8P5615UQA@TSOP56 [CX1055]	K8P6415UQB@FBGA48 [CX5002]
K8P6415UQB@FBGA64 [CX5074]	K8P6415UQB@TSOP48 [CX1004]
K8Q2815UQB@TSOP56 [CX1011]	K8S3015EBF@FBGA44 [CX5099]
K8S3015ETF@FBGA44 [CX5099]	K8S3215EBF@FBGA44 [CX5177]
K8S3215ETF@FBGA44 [CX5177]	K9F1208U0B@TSOP48 [CX1004]

K9F1208U0C@TSOP48 [CX1004]  
K9F1216U0A@TSOP48 [CX1004]  
K9F1G08U0B@TSOP48 [CX1004]  
K9F1G08U0D@TSOP48 [CX1004-3]  
K9F1G16U0M@TSOP48 [CX1004]  
K9F2808U0C@TSOP48 [CX1004]  
K9F2G08U0B@TSOP48 [CX1004-1]  
K9F2G08U0C@TSOP48 [CX1004-3]  
K9F4G08U0A@TSOP48 [CX1004]  
K9F4G08U0D@TSOP48 [CX1004-1]  
K9F5608U0B@TSOP48 [CX1004]  
K9F5608U0C@WSOP48 [CX1004]  
K9F8G08U0M@TSOP48 [CX1004]  
K9G4G08U0B@TSOP48 [CX1004-3]  
K9G8G08U0B@TSOP48 [CX1004-1]  
K9G8G08U0M@TSOP48 [CX1004]  
K9GAG08U0E@TSOP48 [CX1004]  
K9GAG08U0M@TSOP48 [CX1004-1]  
K9GBG08U0B@TSOP48 [CX1004-3]  
K9HBG08U1M@TSOP48 [CX1004]  
K9K1G08U0M@TSOP48 [CX1004]  
K9K4G08U0M@TSOP48 [CX1004]  
K9K8G08U0B@TSOP48 [CX1004-3]  
K9KAG08U0M@TSOP48 [CX1004-1]  
K9LAG08U0M@TSOP48 [CX1004]  
K9LBG08U0M@TSOP48 [CX1004-1]  
K9WAG08U1A@TSOP48 [CX1004]  
K9WAG08U1M@TSOP48 [CX1004]  
K9WBG08U1M1@TSOP48 [CX1004]  
KAD060300B@TBGA69 [CX5001]  
KAD060700D@TBGA69 [CX5001]  
KAD070300C@TBGA69 [CX5001]  
KAD070J00M@TBGA69 [CX5001]  
KAD090300B@TBGA69 [CX5001]  
KFG5616U1A@TSOP48 [CX1004]  
KM2816AI [CX0001]  
KM2817AI [CX0001]  
KM2864AH [CX0001]  
KM2865AH [CX0001]  
KM28C16@PLCC32 [CX2032]  
KM28C16I@PLCC32 [CX2032]  
KM28C17@PLCC32 [CX2032]  
KM28C17I@PLCC32 [CX2032]  
KM28C256@PLCC32 [CX2032]  
KM28C256I@PLCC32 [CX2032]  
KM28C64@PLCC32 [CX2032]  
KM28C64A@PLCC32 [CX2032]  
KM28C64B@PLCC32 [CX2032]  
KM28C64I@PLCC32 [CX2032]  
KM28C65@PLCC32 [CX2032]  
KM28C65A@PLCC32 [CX2032]  
KM28C65I@PLCC32 [CX2032]  
KM93C06(16bit) [CX0001]  
KM93C06(G)(16bit)@SOIC8 [CX1045]  
KM93C06(GD)(08bit)@SOIC8 [CX1045]  
KM93C06(GD)(16bit)@SOIC8 [CX1045]  
KM93C07(08bit) [CX0001]  
KM93C07(G)(08bit)@SOIC8 [CX1045]  
KM93C07(GD)(08bit)@SOIC8 [CX1045]  
K9F1208U0M@TSOP48 [CX1004]  
K9F1G08U0A@TSOP48 [CX1004]  
K9F1G08U0C@TSOP48 [CX1004-1]  
K9F1G08U0M@TSOP48 [CX1004]  
K9F2808U0B@TSOP48 [CX1004]  
K9F2G08U0A@TSOP48 [CX1004]  
K9F2G08U0C@BGA63 [CX5046]  
K9F2G08U0M@TSOP48 [CX1004]  
K9F4G08U0B@TSOP48 [CX1004-1]  
K9F4G08U0M@TSOP48 [CX1004]  
K9F5608U0C@TSOP48 [CX1004]  
K9F5608U0D@TSOP48 [CX1004]  
K9G4G08U0A@TSOP48 [CX1004]  
K9G8G08U0A@TSOP48 [CX1004-1]  
K9G8G08U0C@TSOP48 [CX1004-1]  
K9GAG08U0D@TSOP48 [CX1004-1]  
K9GAG08U0F@TSOP48 [CX1004-3]  
K9GBG08U0A@TSOP48 [CX1004-3]  
K9HBG08U1M(T)@TSOP48 [CX1004]  
K9HCG08U1M@TSOP48 [CX1004]  
K9K2G08U0M@TSOP48 [CX1004]  
K9K8G08U0A@TSOP48 [CX1004]  
K9K8G08U0D@TSOP48 [CX1004-1]  
K9L8G08U0M@TSOP48 [CX1004]  
K9LBG08U0D@TSOP48 [CX1004-1]  
K9T1G08U0M@TSOP48 [CX1004]  
K9WAG08U1B@TSOP48 [CX1004-1]  
K9WBG08U1M@TSOP48 [CX1004-1]  
KAD050300B@TBGA69 [CX5001]  
KAD060300C@TBGA69 [CX5001]  
KAD070300B@TBGA69 [CX5001]  
KAD070700D@TBGA69 [CX5001]  
KAD080300B@TBGA69 [CX5001]  
KAD100300B@TBGA69 [CX5001]  
KM2816A [CX0001]  
KM2817A [CX0001]  
KM2864A [CX0001]  
KM2865A [CX0001]  
KM28C16 [CX0001]  
KM28C16I [CX0001]  
KM28C17 [CX0001]  
KM28C17I [CX0001]  
KM28C256 [CX0001]  
KM28C256I [CX0001]  
KM28C64 [CX0001]  
KM28C64A [CX0001]  
KM28C64B [CX0001]  
KM28C64I [CX0001]  
KM28C65 [CX0001]  
KM28C65A [CX0001]  
KM28C65I [CX0001]  
KM93C06(08bit) [CX0001]  
KM93C06(G)(08bit)@SOIC8 [CX1045]  
KM93C07(16bit) [CX0001]  
KM93C07(G)(16bit)@SOIC8 [CX1045]

KM93C07(GD)(16bit)@SOIC8 [CX1045]  
KM93C46V [CX0001]  
KM93C46V(GD)@SOIC8 [CX1045]  
KM93C47V(G)@SOIC8 [CX1045]  
KM93C56V [CX0001]  
KM93C56V(GD)@SOIC8 [CX1045]  
KM93C57V(G)@SOIC8 [CX1045]  
KM93C66V [CX0001]  
KM93C66V(GD)@SOIC8 [CX1045]  
KM93C67V(G)@SOIC8 [CX1045]  
KS24C010 [CX0001]  
KS24C010@TSSOP8 [CX1059]  
KS24C011@SOIC8 [CX1045]  
KS24C020 [CX0001]  
KS24C020@TSSOP8 [CX1059]  
KS24C021@SOIC8 [CX1045]  
KS24C040 [CX0001]  
KS24C040@TSSOP8 [CX1059]  
KS24C041@SOIC8 [CX1045]  
KS24C080 [CX0001]  
KS24C080@TSSOP8 [CX1059]  
KS24C081@SOIC8 [CX1045]  
S524A40X10 [CX0001]  
S524A40X10@TSSOP8 [CX1059]  
S524A40X11@SOP8 [CX1045]  
S524A40X20 [CX0001]  
S524A40X20@TSSOP8 [CX1059]  
S524A40X21@SOP8 [CX1045]  
S524A40X40 [CX0001]  
S524A40X40@TSSOP8 [CX1059]  
S524A40X41@SOP8 [CX1045]  
S524A60X51 [CX0001]  
S524A60X51@TSSOP8 [CX1059]  
S524A60X81@SOP8 [CX1045]  
S524AB0X91 [CX0001]  
S524AB0X91@TSSOP8 [CX1059]  
S524AB0XB1@SOP8 [CX1045]  
S524AD0XD1 [CX0001]  
S524AD0XD1@TSSOP8 [CX1059]  
S524AD0XF1@SOP8 [CX1045]  
S524C20D11 [CX0001]  
S524C20D11@TSSOP8 [CX1059]  
S524C20D21@SOP8 [CX1045]  
S524C80D41 [CX0001]  
S524C80D41@TSSOP8 [CX1059]  
S524C80D81@SOP8 [CX1045]  
S524L50X51 [CX0001]  
S524L50X51@TSSOP8 [CX1059]  
S524LB0X91@SOP8 [CX1045]  
S524LB0XB1 [CX0001]  
S524LB0XB1@TSSOP8 [CX1059]  
KM93C46V(G)@SOIC8 [CX1045]  
KM93C47V [CX0001]  
KM93C47V(GD)@SOIC8 [CX1045]  
KM93C56V(G)@SOIC8 [CX1045]  
KM93C57V [CX0001]  
KM93C57V(GD)@SOIC8 [CX1045]  
KM93C66V(G)@SOIC8 [CX1045]  
KM93C67V [CX0001]  
KM93C67V(GD)@SOIC8 [CX1045]  
KS24C010@SOIC8 [CX1045]  
KS24C011 [CX0001]  
KS24C011@TSSOP8 [CX1059]  
KS24C020@SOIC8 [CX1045]  
KS24C021 [CX0001]  
KS24C021@TSSOP8 [CX1059]  
KS24C040@SOIC8 [CX1045]  
KS24C041 [CX0001]  
KS24C041@TSSOP8 [CX1059]  
KS24C080@SOIC8 [CX1045]  
KS24C081 [CX0001]  
KS24C081@TSSOP8 [CX1059]  
S524A40X10@SOP8 [CX1045]  
S524A40X11 [CX0001]  
S524A40X11@TSSOP8 [CX1059]  
S524A40X20@SOP8 [CX1045]  
S524A40X21 [CX0001]  
S524A40X21@TSSOP8 [CX1059]  
S524A40X40@SOP8 [CX1045]  
S524A40X41 [CX0001]  
S524A40X41@TSSOP8 [CX1059]  
S524A60X51@SOP8 [CX1045]  
S524A60X81 [CX0001]  
S524A60X81@TSSOP8 [CX1059]  
S524AB0X91@SOP8 [CX1045]  
S524AB0XB1 [CX0001]  
S524AB0XB1@TSSOP8 [CX1059]  
S524AD0XD1@SOP8 [CX1045]  
S524AD0XF1 [CX0001]  
S524AD0XF1@TSSOP8 [CX1059]  
S524C20D11@SOP8 [CX1045]  
S524C20D21 [CX0001]  
S524C20D21@TSSOP8 [CX1059]  
S524C80D41@SOP8 [CX1045]  
S524C80D81 [CX0001]  
S524C80D81@TSSOP8 [CX1059]  
S524L50X51@SOP8 [CX1045]  
S524LB0X91 [CX0001]  
S524LB0X91@TSSOP8 [CX1059]  
S524LB0XB1@SOP8 [CX1045]

#### DRAM & SRAM

KM62256A [CX0001]  
KM62256AL [CX0001]  
KM6264A [CX0001]  
KM6264AL [CX0001]  
KM68257LP [CX0001]  
KM62256A@SOIC28 [CX1035]  
KM62256AL@SOIC28 [CX1035]  
KM6264A@SOIC28 [CX1035]  
KM6264AL@SOIC28 [CX1035]  
KM68257LP@SOIC28 [CX1035]

KM68257P [CX0001]  
KM6865LP [CX0001]  
KM6865P [CX0001]

KM68257P@SOIC28 [CX1035]  
KM6865LP@SOIC28 [CX1035]  
KM6865P@SOIC28 [CX1035]

## PLD

CPL16L8 [CX0001]  
CPL16L8L [CX0001]  
CPL16R4 [CX0001]  
CPL16R4L [CX0001]  
CPL16R6 [CX0001]  
CPL16R6L [CX0001]  
CPL16R8 [CX0001]  
CPL16R8L [CX0001]

CPL16L8@PLCC20 [CX2020]  
CPL16L8L@PLCC20 [CX2020]  
CPL16R4@PLCC20 [CX2020]  
CPL16R4L@PLCC20 [CX2020]  
CPL16R6@PLCC20 [CX2020]  
CPL16R6L@PLCC20 [CX2020]  
CPL16R8@PLCC20 [CX2020]  
CPL16R8L@PLCC20 [CX2020]

## MICROCONTROLLER

S3F8235@PQFP64 [CX3015]  
S3F8235@SDIP64 [CX0064]  
S3F8275@PQFP64 [CX3015]  
S3F8285@PQFP80 [CX3019]  
S3F84I8@QFP44 [CX3046]  
S3F84I9@QFP44 [CX3046]  
S3F84K4@DIP16  
S3F84K4@SOP16 [CX1033]  
S3F84K4@SSOP20 [CX1000]  
S3F84NB@SDIP64 [CX0064]  
S3F84P4@SOP8 [CX1030]  
S3F84U8@SDIP42 [CX0042]  
S3F84UA-SDIP42 [CX0042]  
S3F84VB@SDIP64 [CX0064]  
S3F9444@SOP8 [CX1030]  
S3F9454(dip20)  
S3F9454@SSOP20 [CX1001]  
S3F9488@SDIP32 [CX0032]  
S3F9488@SOP32 [CX1035]  
S3F9498@SDIP32 [CX0032]  
S3F9498@SOP32 [CX1035]  
S3F94A5@SDIP32 [CX0032]  
S3F94C4@DIP20  
S3F94C8@DIP20  
S3P414@QFP44 [CX3046]  
S3P7048@QFP44 [CX3046]  
S3P70F4@SDIP30 [CX0032]  
S3P7224@PQFP64 [CX3015]  
S3P7238@PQFP80 [CX3019]  
S3P72K8@PQFP80 [CX3019]  
S3P72N8@PQFP80 [CX3019]  
S3P72Q5@PQFP100 [CX3023]  
S3P7414@SDIP42 [CX0042]  
S3P7424@SOP28 [CX1033]  
S3P7515@PQFP64 [CX3015]  
S3P7528@QFP44 [CX3046]  
S3P7538@SDIP30 [CX0032]  
S3P7565@PQFP100 [CX3023]  
S3P8245@QFP80 [CX3016]  
S3P8249@QFP80 [CX3016]  
S3P8469@SDIP64 [CX0064]

S3F8235@QFP64 [CX3011]  
S3F8274@QFP48 [CX3007]  
S3F8275@QFP64 [CX3011]  
S3F8285@QFP80 [CX3016]  
S3F84I8@SDIP42 [CX0042]  
S3F84I9@SDIP42 [CX0042]  
S3F84K4@DIP20  
S3F84K4@SOP20 [CX1033]  
S3F84NB@PQFP64 [CX3015]  
S3F84P4  
S3F84U8@QFP44 [CX3046]  
S3F84UA@QFP44 [CX3046]  
S3F84VB@PQFP64 [CX3015]  
S3F9444  
S3F9454(dip16)  
S3F9454@SOP20 [CX1033]  
S3F9488@QFP44 [CX3046]  
S3F9488@SDIP42 [CX0042]  
S3F9498@SDIP30 [CX0032]  
S3F9498@SOP28 [CX1033]  
S3F94A5@QFP44 [CX3046]  
S3F94A5@SDIP42 [CX0042]  
S3F94C4@SOP20 [CX1033]  
S3F94C8@SOP20 [CX1033]  
S3P434@QFP44 [CX3046]  
S3P7048@SDIP42 [CX0042]  
S3P70F4@SOP32 [CX1035]  
S3P7235@PQFP80 [CX3019]  
S3P72F5@PQFP100 [CX3023]  
S3P72N5@PQFP80 [CX3019]  
S3P72P9@PQFP100 [CX3023]  
S3P7335@PQFP80 [CX3019]  
S3P7424@SDIP30 [CX0032]  
S3P7434@SDIP42 [CX0042]  
S3P7515@SDIP64 [CX0064]  
S3P7528@SDIP42 [CX0042]  
S3P7538@SOP32 [CX1035]  
S3P8245@PQFP80 [CX3019]  
S3P8249@PQFP80 [CX3019]  
S3P8469@PQFP64 [CX3015]  
S3P8475@SDIP42 [CX0042]

S3P8475@TQFP44 [CX3046]  
S3P848A@SDIP64 [CX0064]  
S3P9228@SDIP42 [CX0042]  
S3P9234@QFP64 [CX3011]  
S3P9428@SOP28 [CX1033]  
S3P9434(dip16)  
S3P9434(dip20)

S3P848A@PQFP64 [CX3015]  
S3P9228@QFP44 [CX3046]  
S3P9234@PQFP64 [CX3015]  
S3P9428@SDIP30 [CX0032]  
S3P9428@SOP32 [CX1035]  
S3P9434(dip18)  
S3P9434@SOP20 [CX1033]

## SAMSUNG-CUSTOMER

### E (E) PROM/FRAM/NVRAM

K9F1G08U0D(RBA)@TSOP48 [CX1004-3]  
K9F1G08U0D(YINGH)@TSOP48 [CX1004]  
K9GAG08U0F(DIANZ)@TSOP48 [CX1004-3]

## SANYO

### E (E) PROM/FRAM/NVRAM

LE24C041 [CX0001]  
LE24C042 [CX0001]  
LE24C081 [CX0001]  
LE24C082 [CX0001]  
LE24C161 [CX0001]  
LE24C162 [CX0001]  
LE24C322@MFP8 [CX1017]  
LE24CB642M [CX1044]  
LE24L322@MFP8 [CX1017]  
LE25FU106BTT@MSOP8 [CX1017]  
LE25FU406BTT@MSOP8 [CX1017]  
LE25FW056MA@MFP8 [CX1045#1]  
LE25FW106T@MSOP8 [CX1017]  
LE25FW203ATT@MSOP8 [CX1017]  
LE25FW206T@MSOP8 [CX1017]  
LE25FW406BTT@MSOP8 [CX1017]  
LE25FW406T@MSOP8 [CX1017]  
LE25FW806T@MSOP8 [CX1017]  
LE25U40C@USON8 [CX4005#1]  
LE28BW168T@TSOP48 [CX1008]  
LE28C1001AT@TSOP32 [CX1002]  
LE28C1001DT@TSOP32 [CX1002]  
LE28CV1001AM@SOP32 [CX1020]  
LE28CV1001ATS@VSOP32 [CX1003]  
LE28CV1001DTS@VSOP32 [CX1003]  
LE28CW1001DTS@VSOP32 [CX1003]  
LE28DW1621T@TSOP48 [CX1004]  
LE28DW8102T@TSOP48 [CX1008]  
LE28F1101T@TSOP40 [CX1005]  
LE28F1601T(REVERSE)@TSOP40 [CX1005]  
LE28F1601T@TSOP40 [CX1005]  
LE28F4001ATS@TSOP32 [CX1003]  
LE28F8001T(REVERSE)@TSOP40 [CX1005]  
LE28F8001T@TSOP40 [CX1005]  
LE28FV1101T@TSOP40 [CX1005]  
LE28FV1601T(REVERSE)@TSOP40 [CX1005]  
LE28FV1601T@TSOP40 [CX1005]  
LE24C041@MFP8 [CX1017]  
LE24C042@MFP8 [CX1017]  
LE24C081@MFP8 [CX1017]  
LE24C082@MFP8 [CX1017]  
LE24C161@MFP8 [CX1017]  
LE24C162@MFP8 [CX1017]  
LE24C322@WLP6 [CX1041]  
LE24CB642TT [CX1045]  
LE25FU106BMA@MFP8 [CX1017]  
LE25FU406BMA@MFP8 [CX1045#1]  
LE25FW056FN@VSON8 [CX4005#1]  
LE25FW106M@SOP8 [CX1045#1]  
LE25FW1606FN@VSON8 [CX4005#1]  
LE25FW206M@SOP8 [CX1045#1]  
LE25FW406BMA@MFP8 [CX1045#1]  
LE25FW406M@SOP8 [CX1045#1]  
LE25FW806M@SOP8 [CX1045#1]  
LE25U40C@SOP8 [CX1045#1]  
LE26CW006@WLP6 [CX1041]  
LE28C1001AM@SOP32 [CX1020]  
LE28C1001ATS@VSOP32 [CX1003]  
LE28C1001DTS@VSOP32 [CX1003]  
LE28CV1001AT@TSOP32 [CX1002]  
LE28CV1001DT@TSOP32 [CX1002]  
LE28CW1001DT@TSOP32 [CX1002]  
LE28DW1621T@FBGA63 [CX5022]  
LE28DW3218AM@PSOP44 [CX1014]  
LE28DW8163T@TSOP48 [CX1004]  
LE28F2001ATS@TSOP32 [CX1003]  
LE28F4001M@SSOP32 [CX1019]  
LE28FU4101T@TSOP48 [CX1004]  
LE28FV2001ATS@TSOP32 [CX1003]

LE28FV4001ATS@TSOP32 [CX1003]	LE28FV4001CTS@TSOP32 [CX1003]
LE28FV4001M@SSOP32 [CX1019]	LE28FV4001T@TSOP32 [CX1003]
LE28FV4101T@TSOP48 [CX1004]	
LE28FV8001T(REVERSE)@TSOP40 [CX1005]	
LE28FV8001T@TSOP40 [CX1005]	LE28FW1633FB@FBGA48 [CX5002]
LE28FW1633FT@FBGA48 [CX5002]	LE28FW1633TB@TSOP48 [CX1004]
LE28FW1633TT@TSOP48 [CX1004]	LE28FW4101T@TSOP48 [CX1004]
LE28FW8201T@TSOP48 [CX1004]	LE28FW8203TB@FBGA48 [CX5002]
LE28FW8203TB@TSOP48 [CX1004]	LE28FW8203TT@FBGA48 [CX5002]
LE28FW8203TT@TSOP48 [CX1004]	

## MICROCONTROLLER

LC87F2C64A@QFP80 [CX3018]	LC87F2C64A@TQFP80 [CX3016]
LC87F2J04A@QIP48E [CX3093]	LC87F2J04A@SQFP48 [CX3007]
LC87F2J08A@QIP48E [CX3093]	LC87F2J08A@SQFP48 [CX3007]
LC87F2J16A@QIP48E [CX3093]	LC87F2J16A@SQFP48 [CX3007]
LC87F2J32A@QIP48E [CX3093]	LC87F2J32A@SQFP48 [CX3007]
LC87F5G32A@QIP48E [CX3093]	LC87F5G32A@SQFP48 [CX3007]
LC87F5N62B@QIP100E [CX3022]	LC87F5VP6AU@QIP100E [CX3022]

## SCENIX

### MICROCONTROLLER

SX20AC/SS/G@SSOP20 [CX1026]	SX20AC/SS@SSOP20 [CX1026]
SX28AC/DP [CX0001]	SX28AC/DP/G [CX0001]
SX28AC/SS/G@SSOP28 [CX1026]	SX28AC/SS@SSOP28 [CX1026]
SX48BD/G@TQFP48 [CX3047]	SX48BD@TQFP48 [CX3047]

## SEEQ

### E (E) PROM/FRAM/NVRAM

27128 [CX0001]	27256 [CX0001]
2764 [CX0001]	27C256 [CX0001]
2804 [CX0001]	2804A [CX0001]
2816A [CX0001]	2816AH [CX0001]
5213 [CX0001]	52B13 [CX0001]
52B13H [CX0001]	52B23 [CX0001]
52B23H [CX0001]	52B33 [CX0001]
52B33H [CX0001]	5516A [CX0001]
5516AH [CX0001]	5517A [CX0001]
5517AH [CX0001]	DE2817A [CX0001]
DE2817A@PLCC32 [CX2032]	DE2817AH [CX0001]
DE2817AH@PLCC32 [CX2032]	DQ2817A [CX0001]
DQ2817A@PLCC32 [CX2032]	DQ2817AH [CX0001]
DQ2817AH@PLCC32 [CX2032]	DQ2864 [CX0001]
DQ2864@PLCC32 [CX2032]	DQ2864H [CX0001]
DQ2864H@PLCC32 [CX2032]	DQ28C256 [CX0001]
DQ28C256@PLCC32 [CX2032]	DQ28C64 [CX0001]
DQ28C64@PLCC32 [CX2032]	DQ28C64A [CX0001]
DQ28C64A@PLCC32 [CX2032]	DQ28C65 [CX0001]
DQ28C65@PLCC32 [CX2032]	DQ52B13 [CX0001]
DQ52B13H [CX0001]	E28C64 [CX0001]
E28C64@PLCC32 [CX2032]	E52B13 [CX0001]



E52B13H [CX0001]  
E52B23H [CX0001]  
E52B33H [CX0001]  
M28C64@PLCC32 [CX2032]  
M52B13H [CX0001]  
M52B23H [CX0001]  
M52B33H [CX0001]  
PQ2864@PLCC32 [CX2032]  
PQ2864H@PLCC32 [CX2032]  
PQ28C64@PLCC32 [CX2032]  
PQ28C65@PLCC32 [CX2032]

E52B23 [CX0001]  
E52B33 [CX0001]  
M28C64 [CX0001]  
M52B13 [CX0001]  
M52B23 [CX0001]  
M52B33 [CX0001]  
PQ2864 [CX0001]  
PQ2864H [CX0001]  
PQ28C64 [CX0001]  
PQ28C65 [CX0001]

## PLD

PALCE26V12H/4 [CX0001]  
PALCE26V12H/4@SOIC28 [CX1033]  
PALCE26V12H-15@PLCC28 [CX0001]  
PALCE26V12H-20 [CX0001]  
PALCE26V12H-20@SOIC28 [CX0001]  
PALCE26V12H-25@PLCC28 [CX0001]

PALCE26V12H/4@PLCC28 [CX2028]  
PALCE26V12H-15 [CX0001]  
PALCE26V12H-15@SOIC28 [CX0001]  
PALCE26V12H-20@PLCC28 [CX0001]  
PALCE26V12H-25 [CX0001]  
PALCE26V12H-25@SOIC28 [CX0001]

## SEIKO

### E (E) PROM/FRAM/NVRAM

S-22H10 [CX0001]  
S-22H12 [CX0001]  
S-22S10 [CX0001]  
S-22S12 [CX0001]  
S-24C01A(DP) [CX0001]  
S-24C01A(FJA)@SOIC8 [CX1045]  
S-24C01B(FJ)@SOIC8 [CX1045]  
S-24C01CFM [CX0001]  
S-24C01CPH [CX0001]  
S-24C02A(DPA) [CX0001]  
S-24C02B(DP) [CX0001]  
S-24C02CFJ [CX1045]  
S-24C02CFT [CX1059]  
S-24C04A(DP) [CX0001]  
S-24C04A(FJA)@SOIC8 [CX1045]  
S-24C04B(FJ)@SOIC8 [CX1045]  
S-24C04CFM [CX0001]  
S-24C04CPH [CX0001]  
S-24C08A(FJA)@SOIC8 [CX1045]  
S-24C08CFM [CX0001]  
S-24C08CPH [CX0001]  
S-24C128CFM [CX0001]  
S-24C128CPH [CX0001]  
S-24C16A(FJA)@SOIC8 [CX1045]  
S-24C16CFM [CX0001]  
S-24C16CPH [CX0001]  
S-24C256CFM [CX0001]  
S-24C256CPH [CX0001]  
S-24C32CFM [CX0001]  
S-24C32CPH [CX0001]  
S-24C512C-T8 [CX1059]  
S-24C64CFM [CX0001]

S-22H10@SOP18 [CX1033]  
S-22H12@SOP18 [CX1033]  
S-22S10@SOP18 [CX1033]  
S-22S12@SOP18 [CX1033]  
S-24C01A(DPA) [CX0001]  
S-24C01B(DP) [CX0001]  
S-24C01CFJ [CX1045]  
S-24C01CFT [CX1059]  
S-24C02A(DP) [CX0001]  
S-24C02A(FJA)@SOIC8 [CX1045]  
S-24C02B(FJ)@SOIC8 [CX1045]  
S-24C02CFM [CX0001]  
S-24C02CPH [CX0001]  
S-24C04A(DPA) [CX0001]  
S-24C04B(DP) [CX0001]  
S-24C04CFJ [CX1045]  
S-24C04CFT [CX1059]  
S-24C08A(DPA) [CX0001]  
S-24C08CFJ [CX1045]  
S-24C08CFT [CX1059]  
S-24C128CFJ [CX1045]  
S-24C128CFT [CX1045]  
S-24C16A(DPA) [CX0001]  
S-24C16CFJ [CX1045]  
S-24C16CFT [CX1059]  
S-24C256CFJ [CX1045]  
S-24C256CFT [CX1045]  
S-24C32CFJ [CX1045]  
S-24C32CFT [CX1045]  
S-24C512C-S8 [CX1044]  
S-24C64CFJ [CX1045]  
S-24C64CFT [CX1045]

S-24C64CPH [CX0001]  
S-24CS01A(DP) [CX0001]  
S-24CS01A(FT)@TSSOP8 [CX1059]  
S-24CS02A(FJ)@SOIC8 [CX1045]  
S-24CS04A(DP) [CX0001]  
S-24CS04A(FT)@TSSOP8 [CX1059]  
S-24CS08A(FJ)@SOIC8 [CX1045]  
S-24CS16A(DP) [CX0001]  
S-24CS16A(FT)@TSSOP8 [CX1059]  
S-24CS64A(FT)@TSSOP8 [CX1059]  
S-24H30@SOP8 [CX1079]  
S-24H45@SOP8 [CX1079]  
S-24S30@SOP8 [CX1079]  
S-24S45@SOP8 [CX1079]  
S-25A020A@SOP8 [CX1045]  
S-25A080A@SOP8 [CX1045]  
S-25A320A@SOP8 [CX1045]  
S-25C010A@SOP8 [CX1045]  
S-25C020A@SOP8 [CX1045]  
S-25C040A@SOP8 [CX1045]  
S-25C080A@SOP8 [CX1045]  
S-25C128A@SOP8 [CX1045#1]  
S-25C160A@SOP8 [CX1045]  
S-25C256A@SOP8 [CX1045#1]  
S-25C320A@SOP8 [CX1045]  
S-25C512A@SOP8 [CX1045]  
S-25C640A@SOP8 [CX1045]  
S-25CM01A@SOP8 [CX1045]  
S-2900A(DP) [CX0001]  
S-2900A(UP)@SOT-89-5 [CX1041]  
S-29130A(DFJA)@SOIC8 [CX1045]  
S-29130A(FJA)@SOIC8 [CX1045]  
S-29131A(FJA)@SOIC8 [CX1045]  
S-29190A(FJA)@SOIC8 [CX1045]  
S-29191A(FJA)@SOIC8 [CX1045]  
S-29194A(FJA)@SOIC8 [CX1045]  
S-29220A(DPA) [CX0001]  
S-29221A(DPA) [CX0001]  
S-29230A(DFJA)@SOIC8 [CX1045]  
S-29230A(FJA)@SOIC8 [CX1045]  
S-29231A(FJA)@SOIC8 [CX1045]  
S-29290A(FJA)@SOIC8 [CX1045]  
S-29291A(FJA)@SOIC8 [CX1045]  
S-29294A(FJA)@SOIC8 [CX1045]  
S-29330A(DPA) [CX0001]  
S-29331A(DPA) [CX0001]  
S-29390A(DPA) [CX0001]  
S-29391A(DPA) [CX0001]  
S-29394A(DPA) [CX0001]  
S-29430A [CX0001]  
S-29530A [CX0001]  
S-29630A [CX0001]  
S-29L130A(DFE)@SOIC8 [CX1045]  
S-29L130A(FS)@SSOP8 [CX1059]  
S-29L131A(FS)@SSOP8 [CX1059]  
S-29L194A(FS)@TSSOP8 [CX1059]  
S-29L220A(FE)@SOIC8 [CX1045]  
S-29L221A(DFE)@SOIC8 [CX1045]  
S-29L294A(DFE)@SOIC8 [CX1045]  
S-24CM01C-S8 [CX1045]  
S-24CS01A(FJ)@SOIC8 [CX1045]  
S-24CS02A(DP) [CX0001]  
S-24CS02A(FT)@TSSOP8 [CX1059]  
S-24CS04A(FJ)@SOIC8 [CX1045]  
S-24CS08A(DP) [CX0001]  
S-24CS08A(FT)@TSSOP8 [CX1059]  
S-24CS16A(FJ)@SOIC8 [CX1045]  
S-24CS64A(FJ)@SOIC8 [CX1045]  
S-24H30 [CX0001]  
S-24H45 [CX0001]  
S-24S30 [CX0001]  
S-24S45 [CX0001]  
S-25A010A@SOP8 [CX1045]  
S-25A040A@SOP8 [CX1045]  
S-25A160A@SOP8 [CX1045]  
S-25A640A@SOP8 [CX1045]  
S-25C010A@TSSOP8 [CX1059]  
S-25C020A@TSSOP8 [CX1059]  
S-25C040A@TSSOP8 [CX1059]  
S-25C080A@TSSOP8 [CX1059]  
S-25C128A@TSSOP8 [CX1059#1]  
S-25C160A@TSSOP8 [CX1059]  
S-25C256A@TSSOP8 [CX1059#1]  
S-25C320A@TSSOP8 [CX1059]  
S-25C512A@TSSOP8 [CX1059]  
S-25C640A@TSSOP8 [CX1059]  
S-2817A@SOP28 [CX1033]  
S-2900A(FE)@SOP8 [CX1045]  
S-2911(DP) [CX0001]  
S-29130A(DPA) [CX0001]  
S-29131A(DPA) [CX0001]  
S-29190A(DPA) [CX0001]  
S-29191A(DPA) [CX0001]  
S-29194A(DPA) [CX0001]  
S-29220A(DFJA)@SOIC8 [CX1045]  
S-29220A(FJA)@SOIC8 [CX1045]  
S-29221A(FJA)@SOIC8 [CX1045]  
S-29230A(DPA) [CX0001]  
S-29231A(DPA) [CX0001]  
S-29290A(DPA) [CX0001]  
S-29291A(DPA) [CX0001]  
S-29294A(DPA) [CX0001]  
S-29330A(DFJA)@SOIC8 [CX1045]  
S-29330A(FJA)@SOIC8 [CX1045]  
S-29331A(FJA)@SOIC8 [CX1045]  
S-29390A(FJA)@SOIC8 [CX1045]  
S-29391A(FJA)@SOIC8 [CX1045]  
S-29394A(FJA)@SOIC8 [CX1045]  
S-29430A@SOIC8 [CX1045]  
S-29530A@SOIC8 [CX1045]  
S-29630A@SOIC8 [CX1045]  
S-29L130A(FE)@SOIC8 [CX1045]  
S-29L131A(DFE)@SOIC8 [CX1045]  
S-29L194A(DFE)@SOIC8 [CX1045]  
S-29L220A(DFE)@SOIC8 [CX1045]  
S-29L220A(FS)@SSOP8 [CX1059]  
S-29L221A(FS)@SSOP8 [CX1059]  
S-29L294A(FS)@TSSOP8 [CX1059]

S-29L330A(DFE)@SOIC8 [CX1045]  
S-29L330A(FS)@SSOP8 [CX1059]  
S-29L331A(FS)@SSOP8 [CX1059]  
S-29L394A(FS)@TSSOP8 [CX1059]  
S-29U130A(FS)@SSOP8 [CX1059]  
S-29U131A(FS)@SSOP8 [CX1059]  
S-29U194A(FS)@TSSOP8 [CX1059]  
S-29U220A(FS)@SSOP8 [CX1059]  
S-29U221A(FS)@SSOP8 [CX1059]  
S-29U294A(FS)@TSSOP8 [CX1059]  
S-29U330A(FS)@SSOP8 [CX1059]  
S-29U331A(FS)@SSOP8 [CX1059]  
S-29U394A(FS)@TSSOP8 [CX1059]  
S-29Z330A(FS)@SSOP8 [CX1059]  
S-29Z430A(FS)@SSOP8 [CX1059]  
S-93A56A(D0A)@SOIC8 [CX1045]  
S-93A66A(FJ)@SOIC8 [CX1045]  
S-93C46A(DFJ)@SOIC8 [CX1045]  
S-93C46A(FJ)@SOIC8 [CX1045]  
S-93C46B(DP) [CX0001]  
S-93C46B(FT)@TSSOP8 [CX1059]  
S-93C56A(DP) [CX0001]  
S-93C56A(FT)@TSSOP8 [CX1059]  
S-93C56B(FJ)@SOIC8 [CX1045]  
S-93C66A(DFJ)@SOIC8 [CX1045]  
S-93C66A(FJ)@SOIC8 [CX1045]  
S-93C66B(DP) [CX0001]  
S-93C66B(FT)@TSSOP8 [CX1059]  
S-93C76A(FJ)@SOIC8 [CX1045]  
S-93C86A(DP) [CX0001]  
S-93C86A(FT)@TSSOP8 [CX1059]  
S-93C86B@TSSOP8 [CX1059]  
S-93L46A(D0I)@TMSOP8 [CX1015]  
S-93L46A(R0I)@SOIC8 [CX1045]  
S-93L56A(D0I)@TMSOP8 [CX1015]  
S-93L56A(R0I)@SOIC8 [CX1045]  
S-93L66A(D0I)@TMSOP8 [CX1015]  
S-93L66A(R0I)@SOIC8 [CX1045]  
S-93L76A(D0I)@TMSOP8 [CX1015]

S-29L330A(FE)@SOIC8 [CX1045]  
S-29L331A(DFE)@SOIC8 [CX1045]  
S-29L394A(DFE)@SOIC8 [CX1045]  
S-29U130A(DFE)@SOIC8 [CX1045]  
S-29U131A(DFE)@SOIC8 [CX1045]  
S-29U194A(DFE)@SOIC8 [CX1045]  
S-29U220A(DFE)@SOIC8 [CX1045]  
S-29U221A(DFE)@SOIC8 [CX1045]  
S-29U294A(DFE)@SOIC8 [CX1045]  
S-29U330A(DFE)@SOIC8 [CX1045]  
S-29U331A(DFE)@SOIC8 [CX1045]  
S-29U394A(DFE)@SOIC8 [CX1045]  
S-29Z330A(DFJA)@SOIC8 [CX1045]  
S-29Z430A(DFJA)@SOIC8 [CX1045]  
S-93A46A(D0A)@SOIC8 [CX1045]  
S-93A66A(D0A)@SOIC8 [CX1045]  
S-93A86A@SOIC8 [CX1045]  
S-93C46A(DP) [CX0001]  
S-93C46A(FT)@TSSOP8 [CX1059]  
S-93C46B(FJ)@SOIC8 [CX1045]  
S-93C56A(DFJ)@SOIC8 [CX1045]  
S-93C56A(FJ)@SOIC8 [CX1045]  
S-93C56B(DP) [CX0001]  
S-93C56B(FT)@TSSOP8 [CX1059]  
S-93C66A(DP) [CX0001]  
S-93C66A(FT)@TSSOP8 [CX1059]  
S-93C66B(FJ)@SOIC8 [CX1045]  
S-93C76A(DP) [CX0001]  
S-93C76A(FT)@TSSOP8 [CX1059]  
S-93C86A(FJ)@SOIC8 [CX1045]  
S-93C86B@SOIC8 [CX1045]  
S-93L46A(D0I)@SOIC8 [CX1045]  
S-93L46A(D0I)@TSSOP8 [CX1059]  
S-93L56A(D0I)@SOIC8 [CX1045]  
S-93L56A(D0I)@TSSOP8 [CX1059]  
S-93L66A(D0I)@SOIC8 [CX1045]  
S-93L66A(D0I)@TSSOP8 [CX1059]  
S-93L76A(D0I)@SOIC8 [CX1045]  
S-93L76A(D0I)@TSSOP8 [CX1059]

## SGS-THOMSON

### E (E) PROM/FRAM/NVRAM

ET2716 [CX0001]  
ETC2732 [CX0001]  
M24128@SOIC8 [CX1045]  
M24164@SOIC8 [CX1045]  
M24256[3.9]@SOIC8 [CX1045]  
M24512 [CX0001]  
M24512@TSOP8 [CX1059]  
M24C04@SOIC8 [CX1045]  
M24C08@SOIC8 [CX1045]  
M24C08W@SOIC8 [CX1045]  
M24C64(BN) [CX0001]  
M24C64(DW)@TSSOP8 [CX1045]  
M24C64(MW)@SOIC8 [CX1045]  
M2716 [CX0001]

ETC2716 [CX0001]  
M24128 [CX0001]  
M24164 [CX0001]  
M24256 [CX0001]  
M24256[5.5]@SOIC8 [CX1031]  
M24512@SOIC8 [CX1044]  
M24C04 [CX0001]  
M24C08 [CX0001]  
M24C08W [CX0001]  
M24C08W@TSOP8 [CX1059]  
M24C64(DL)@TSSOP14 [CX1000]  
M24C64(MN)@SOIC8 [CX1031]  
M27128A [CX0001]  
M27256 [CX0001]

M27256A [CX0001]  
M27512 [CX0001]  
M2764A [CX0001]  
M27C1000@PLCC32 [CX2032]  
M27C1001 [CX0001]  
M27C1001@TSOP32 [CX1002]  
M27C1024@PLCC44 [CX2044]  
M27C160@PLCC44 [CX2044]  
M27C2001 [CX0001]  
M27C2001@TSOP32 [CX1002]  
M27C202@PLCC44 [CX2044]  
M27C256B [CX0001]  
M27C400 [CX0001]  
M27C4001@PLCC32 [CX2032]  
M27C4002 [CX0001]  
M27C405 [CX0001]  
M27C405@TSOP32 [CX1002]  
M27C512@PLCC32 [CX2032]  
M27C516@PLCC44 [CX2044]  
M27C64A@PLCC32 [CX2032]  
M27C800@PLCC44 [CX2044]  
M27C801 [CX0001]  
M27C801@TSOP32 [CX1002]  
M27HC641@PLCC28 [CX2028]  
M27HC642@PLCC28 [CX2028]  
M27V101@PLCC32 [CX2032]  
M27V201 [CX0001]  
M27V201@TSOP32 [CX1002]  
M27V401@PLCC32 [CX2032]  
M27V402 [CX0001]  
M27V402@TSOP40 [CX1006]  
M27V512@PLCC32 [CX2032]  
M27V800 [CX0001]  
M27V801 [CX0001]  
M27V801@TSOP32 [CX1002]  
M27W201@PLCC32 [CX2032]  
M28010 [CX0001]  
M28010@TSOP32 [CX1002]  
M28C64C [CX0001]  
M28C64C@SOIC28 [CX1033]  
M28F101 [CX0001]  
M28F101@PLCC32 [CX2032]  
M28F102 [CX0001]  
M28F102@TSOP40 [CX1005]  
M28F151(REVERSE)@TSOP32 [CX1002]  
M28F151@TSOP32 [CX1002]  
M28F201(REVERSE)@TSOP32 [CX1002]  
M28F201@TSOP32 [CX1002]  
M28F210@TSOP48 [CX1004]  
M28F220@PSOP44 [CX1014]  
M28F221@TSOP40 [CX1006]  
M28F256(REVERSE)@TSOP32 [CX1002]  
M28F256@TSOP32 [CX1002]  
M28F421@TSOP40 [CX1006]  
M28F512(REVERSE)@TSOP32 [CX1002]  
M28F512@TSOP32 [CX1002]  
M29F002B@PLCC32 [CX2032]  
M29F002T [CX0001]  
M29F002T@TSOP32 [CX1002]  
M2732A [CX0001]  
M2764 [CX0001]  
M27C1000 [CX0001]  
M27C1000@TSOP32 [CX1002]  
M27C1001@PLCC32 [CX2032]  
M27C1024 [CX0001]  
M27C160 [CX0001]  
M27C160@PSOP44 [CX1014]  
M27C2001@PLCC32 [CX2032]  
M27C202 [CX0001]  
M27C202@VSOP40 [CX1005]  
M27C256B@PLCC32 [CX2032]  
M27C4001 [CX0001]  
M27C4001@TSOP32 [CX1002]  
M27C4002@PLCC44 [CX0001]  
M27C405@PLCC32 [CX2032]  
M27C512 [CX0001]  
M27C516 [CX0001]  
M27C64A [CX0001]  
M27C800 [CX0001]  
M27C800@PSOP44 [CX1014]  
M27C801@PLCC32 [CX2032]  
M27HC641 [CX0001]  
M27HC642 [CX0001]  
M27V101 [CX0001]  
M27V101@TSOP32 [CX1002]  
M27V201@PLCC32 [CX2032]  
M27V401 [CX0001]  
M27V401@TSOP32 [CX1002]  
M27V402@PLCC44 [CX2044]  
M27V512 [CX0001]  
M27V512@TSOP28 [CX1024]  
M27V800@PLCC44 [CX2044]  
M27V801@PLCC32 [CX2032]  
M27W201 [CX0001]  
M27W201@TSOP32 [CX1002]  
M28010@PLCC32 [CX2032]  
M28C16@PLCC32 [CX2032]  
M28C64C@PLCC32 [CX2032]  
M28C64C@TSOP28 [CX1024]  
M28F101(REVERSE)@TSOP32 [CX1002]  
M28F101@TSOP32 [CX1002]  
M28F102@PLCC44 [CX2044]  
M28F151 [CX0001]  
M28F151@PLCC32 [CX2032]  
M28F201 [CX0001]  
M28F201@PLCC32 [CX2032]  
M28F210@PSOP44 [CX1014]  
M28F211@TSOP40 [CX1006]  
M28F220@TSOP48 [CX1004]  
M28F256 [CX0001]  
M28F256@PLCC32 [CX2032]  
M28F411@TSOP40 [CX1006]  
M28F512 [CX0001]  
M28F512@PLCC32 [CX2032]  
M29F002B [CX0001]  
M29F002B@TSOP32 [CX1002]  
M29F002T@PLCC32 [CX2032]  
M29F040 [CX0001]

M29F040@PLCC32 [CX2032]  
M29F040B [CX0001]  
M29F040B@TSOP32 [CX1002]  
M29F100B@TSOP48 [CX1004]  
M29F100T@TSOP48 [CX1004]  
M29F102B@TSOP40 [CX1005]  
M29F102BB@TSOP40 [CX1005]  
M29F200B@TSOP48 [CX1004]  
M29F200T@TSOP48 [CX1004]  
M29F400B@TSOP48 [CX1004]  
M29F400T@TSOP48 [CX1004]  
M29V040@TSOP32 [CX1002]  
M29W008T@TSOP40 [CX1006]  
M29W040@TSOP32 [CX1002]  
M29W400B@TSOP48 [CX1004]  
M29W400T@TSOP48 [CX1004]  
M29W512B@TSOP32 [CX1003]  
M29W800B@TSOP48 [CX1004]  
M29W800T@TSOP48 [CX1004]  
M48T35@SOIC28 [CX1033]  
M48T35Y@SOIC28 [CX1033]  
M48T59@SOIC28 [CX1033]  
M48T59Y@SOIC28 [CX1033]  
M48Z128Y [CX0001]  
M48Z30Y [CX0001]  
M48Z32Y [CX0001]  
M50FW080@TSOP40 [CX1006]  
M87C257 [CX0001]  
M93C06(08bit) [CX0001]  
M93C06(16bit) [CX0001]  
M93S46 [CX0001]  
M93S46@TSSOP8  
M95P02@SOIC8 [CX1045]  
M95P04@SOIC8 [CX1045]  
M95P08@SOIC8 [CX1045]  
MK48C02B [CX0001]  
MK48C12B [CX0001]  
MK48T02B [CX0001]  
MK48T12 [CX0001]  
MK48T18 [CX0001]  
MK48Z02B [CX0001]  
MK48Z12 [CX0001]  
MK48Z18 [CX0001]  
MKI48Z02B [CX0001]  
MKI48Z12B [CX0001]  
ST24C01 [CX0001]  
ST24C02A [CX0001]  
ST24C16 [CX0001]  
ST24W01 [CX0001]  
ST24W02 [CX0001]  
ST24W04C [CX0001]  
ST27128A [CX0001]  
ST2764A [CX0001]  
ST93C06(08bit) [CX0001]  
ST93C06(16bit) [CX0001]  
ST93CS46 [CX0001]  
TS27C256 [CX0001]  
TS27C64@PLCC32 [CX2032]  
TS27C64A@PLCC32 [CX2032]

M29F040@TSOP32 [CX1002]  
M29F040B@PLCC32 [CX2032]  
M29F100B@PSOP44 [CX1014]  
M29F100T@PSOP44 [CX1014]  
M29F102B@PLCC44 [CX2044]  
M29F102BB@PLCC44 [CX2044]  
M29F200B@PSOP44 [CX1014]  
M29F200T@PSOP44 [CX1014]  
M29F400B@PSOP44 [CX1014]  
M29F400T@PSOP44 [CX1014]  
M29V040@PLCC32 [CX2032]  
M29W008B@TSOP40 [CX1006]  
M29W040@PLCC32 [CX2032]  
M29W400B@PSOP44 [CX1014]  
M29W400T@PLCC44 [CX1014]  
M29W512B@PLCC32 [CX2032]  
M29W800B@PSOP44 [CX1014]  
M29W800T@PSOP44 [CX1014]  
M48T35 [CX0001]  
M48T35Y [CX0001]  
M48T59 [CX0001]  
M48T59Y [CX0001]  
M48Z128 [CX0001]  
M48Z30 [CX0001]  
M48Z32 [CX0001]  
M50FW080@PLCC32 [CX2032]  
M50FW080@VSOP32 [CX1003]  
M87C257@PLCC32 [CX2032]  
M93C06(08bit)@SOIC8 [CX1045]  
M93C06(16bit)@SOIC8 [CX1045]  
M93S46@SOIC8 [CX1045]  
M95P02 [CX0001]  
M95P04 [CX0001]  
M95P08 [CX0001]  
MK48C02 [CX0001]  
MK48C12 [CX0001]  
MK48T02 [CX0001]  
MK48T08 [CX0001]  
MK48T12B [CX0001]  
MK48Z02 [CX0001]  
MK48Z08 [CX0001]  
MK48Z12B [CX0001]  
MKI48Z02 [CX0001]  
MKI48Z12 [CX0001]  
MKI48Z18 [CX0001]  
ST24C01@SOIC8 [CX1045]  
ST24C02A@SOIC8 [CX1045]  
ST24C16@SOIC8 [CX1045]  
ST24W01@SOIC8 [CX1045]  
ST24W02@SOIC8 [CX1045]  
ST24W04C@SOIC8 [CX1045]  
ST27256 [CX0001]  
ST27C256 [CX0001]  
ST93C06(08bit)@SOIC8 [CX1045]  
ST93C06(16bit)@SOIC8 [CX1045]  
ST93CS46@SOIC8 [CX1045]  
TS27C64 [CX0001]  
TS27C64A [CX0001]  
TS28C16A [CX0001]

TS28C17A [CX0001]

## PLD

GAL16V8 [CX0001]

GAL16V8A [CX0001]

## SHARP

### E(E) PROM/FRAM/NVRAM

LH28F002SCHN@PSOP44 [CX1014]	LH28F002SCHT@TSOP40 [CX1006]
LH28F002SCN@PSOP44 [CX1014]	LH28F002SCT@TSOP40 [CX1006]
LH28F004BVE(BT)@TSOP40 [CX1006]	LH28F004BVE(TT)@TSOP40 [CX1006]
LH28F004BVHS(BT)@VSOP40 [CX1005]	LH28F004BVHS(TT)@VSOP40 [CX1005]
LH28F004BVT(BT)@TSOP40 [CX1006]	LH28F004BVT(TT)@TSOP40 [CX1006]
LH28F004SCHN@PSOP44 [CX1014]	LH28F004SCHS@VSOP40 [CX1005]
LH28F004SCHT@TSOP40 [CX1006]	LH28F004SCN@PSOP44 [CX1014]
LH28F004SCS@VSOP40 [CX1005]	LH28F004SCT@TSOP40 [CX1006]
LH28F008BJT(BTLZ1)@TSOP40 [CX1006]	
LH28F008BJT(TB)@TSOP40 [CX1006]	LH28F008BJT(TT)@TSOP40 [CX1006]
LH28F008BJT(TTLZ2)@TSOP40 [CX1006]	
LH28F008BVT(BT)@TSOP40 [CX1006]	LH28F008BVT(TT)@TSOP40 [CX1006]
LH28F008SAN@PSOP44 [CX1014]	LH28F008SAR@RTSOP40 [CX1006]
LH28F008SAT@TSOP40 [CX1006]	
LH28F008SCH(L85)@RTSOP40 [CX1006]	
LH28F008SCH-L@TSOP40 [CX1006]	LH28F008SCHN@PSOP44 [CX1014]
LH28F008SCH-V@TSOP40 [CX1006]	
LH28F008SCH-ZU-120@TSOP40 [CX1006]	
LH28F008SCN@PSOP44 [CX1014]	LH28F008SCN-L@PSOP44 [CX1014]
LH28F008SCT@TSOP40 [CX1006]	LH28F008SCT-L@TSOP40 [CX1006]
LH28F008SCT-V@TSOP40 [CX1006]	LH28F008SCV@TSOP40 [CX1006]
LH28F016SA@TSOP56 [CX1055]	LH28F016SC@PSOP44 [CX1014]
LH28F016SCR(L95)@RTSOP40 [CX1006]	
LH28F016SCT-L95@TSOP40 [CX1006]	LH28F016SUT@TSOP56 [CX1011]
LH28F128BFHBD@CSP72 [CX5001]	LH28F128BFHE@TSOP48 [CX1004]
LH28F128BFHT(PBTL70_75A)@TSOP56 [CX1011]	
LH28F128BFHT(PTTL70_75A)@TSOP56 [CX1011]	
LH28F128BFHT(PTTLITA)@TSOP56 [CX1011]	
LH28F128BFHT(PWTL80)@TSOP56 [CX1011]	
LH28F128BFND@PSOP44 [CX1014]	LH28F128SPHTD@TSOP56 [CX1055]
LH28F160BGB(B)@CSP48 [CX50UN]	LH28F160BGB(T)@CSP48 [CX50UN]
LH28F160BGE(B)@TSOP48 [CX1004]	LH28F160BGE(T)@TSOP48 [CX1004]
LH28F160BHBB@FBGA48 [CX50UN]	LH28F160BHBT@FBGA48 [CX50UN]
LH28F160BHEB@TSOP48 [CX1004]	LH28F160BHET@TSOP48 [CX1004]
LH28F160BJBB@FBGA48 [CX50UN]	LH28F160BJBT@FBGA48 [CX50UN]
LH28F160BJD [CX0001]	LH28F160BJEB@TSOP48 [CX1004]
LH28F160BJET@TSOP48 [CX1004]	LH28F160BJHBB@FBGA48 [CX50UN]
LH28F160BJHBT@FBGA48 [CX50UN]	
LH28F160BJHE(BTLZD)@TSOP48 [CX1004]	
LH28F160BJHE(TTLZD)@TSOP48 [CX1004]	
LH28F160BJHEB@TSOP48 [CX1004]	LH28F160BJHET@TSOP48 [CX1004]
LH28F160BJHGB@FBGA48 [CX50UN]	LH28F160BJHGT@FBGA48 [CX50UN]
LH28F160BVE(BTL)@TSOP48 [CX1004]	LH28F160BVE(TTL)@TSOP48 [CX1004]
LH28F160BVEB(B)@CSP48 [CX50UN]	LH28F160BVEB(T)@CSP48 [CX50UN]
LH28F160BVHE(BTL)@TSOP48 [CX1004]	
LH28F160BVHE(TTL)@TSOP48 [CX1004]	
LH28F160S3HNS@SSOP56 [CX1029]	LH28F160S3HT@TSOP56 [CX1055]

LH28F160S3NS@SSOP56 [CX1029]                    LH28F160S3T@TSOP56 [CX1055]  
LH28F160S5HNS@SSOP56 [CX1029]                    LH28F160S5HT@TSOP56 [CX1055]  
LH28F160S5NS@SSOP56 [CX1029]                    LH28F160S5T@TSOP56 [CX1055]  
LH28F160SKT@TSOP56 [CX1055]                    LH28F320BFB(PB)@FBGA48 [CX5005]  
LH28F320BFB(PT)@FBGA48 [CX5005]                    LH28F320BFE(PB)@TSOP48 [CX1004]  
LH28F320BFE(PT)@TSOP48 [CX1004]                    LH28F320BFHB(PB)@FBGA48 [CX5005]  
LH28F320BFHB(PT)@FBGA48 [CX5005]                    LH28F320BFHE(PB)@TSOP48 [CX1004]  
LH28F320BFHE(PBTLZ2)@TSOP48 [CX1004]  
LH28F320BFHE(PBTLZA)@TSOP48 [CX1004]  
LH28F320BFHE(PT)@TSOP48 [CX1004]  
LH28F320BFHE(PTTLE0)@TSOP48 [CX1004]  
LH28F320BFHE(PTTLZ1)@TSOP48 [CX1004]  
LH28F320BFHE(PTTLZ9)@TSOP48 [CX1004]  
LH28F320BFHG(PBTLZL)@FBGA48 [CX5080]  
LH28F320BFHG(PBTLZN)@FBGA48 [CX5080]  
LH28F320BFHG(PTTLZ3)@FBGA48 [CX5080]  
LH28F320BFHG(PTTLZK)@FBGA48 [CX5080]  
LH28F320BFHG(PTTLZM)@FBGA48 [CX5080]  
LH28F320BFN@PSOP44 [CX1014]                    LH28F320BJD [CX0001]  
LH28F320BJE(PB)(OTP)@TSOP48 [CX1004]  
LH28F320BJE(PB)@TSOP48 [CX1004]  
LH28F320BJE(PT)(OTP)@TSOP48 [CX1004]  
LH28F320BJE(PT)@TSOP48 [CX1004]  
LH28F320BJHE(PB)(OTP)@TSOP48 [CX1004]  
LH28F320BJHE(PT)(OTP)@TSOP48 [CX1004]  
LH28F320BJN@PSOP44 [CX1014]                    LH28F320BMN@PSOP44 [CX1014]  
LH28F320S3HNS@SSOP56 [CX1029]                    LH28F320S3HT@TSOP56 [CX1055]  
LH28F320S3NS@SSOP56 [CX1029]                    LH28F320S3T@TSOP56 [CX1055]  
LH28F320S3TD@TSOP56 [CX1055]                    LH28F320S5HNS@SSOP56 [CX1029]  
LH28F320S5HT@TSOP56 [CX1055]                    LH28F320S5NS@SSOP56 [CX1029]  
LH28F320S5T@TSOP56 [CX1055]                    LH28F320SKTD@TSOP56 [CX1055]  
LH28F320SUTD@TSOP56 [CX1055]                    LH28F400BGB(B)@CSP48 [CX50UN]  
LH28F400BGB(T)@CSP48 [CX50UN]                    LH28F400BGE(B)@TSOP48 [CX1004]  
LH28F400BGE(T)@TSOP48 [CX1004]                    LH28F400BGHB(B)@CSP48 [CX50UN]  
LH28F400BGHB(T)@CSP48 [CX50UN]                    LH28F400BGHE(B)@TSOP48 [CX1004]  
LH28F400BGHE(T)@TSOP48 [CX1004]                    LH28F400BGN(B)@PSOP44 [CX1014]  
LH28F400BGN(T)@PSOP44 [CX1014]                    LH28F400BVB(B)@CSP48 [CX50UN]  
LH28F400BVB(T)@CSP48 [CX50UN]                    LH28F400BVE(B)@TSOP48 [CX1004]  
LH28F400BVE(T)@TSOP48 [CX1004]                    LH28F400BVHB(B)@CSP48 [CX50UN]  
LH28F400BVHB(T)@CSP48 [CX50UN]                    LH28F400BVHE(B)@TSOP48 [CX1004]  
LH28F400BVHE(T)@TSOP48 [CX1004]                    LH28F400BVN(B)@PSOP44 [CX1014]  
LH28F400BVN(T)@PSOP44 [CX1014]  
LH28F512BFBD(PTSLZ2)@CSP72 [CX5001]  
LH28F512BFBD(PTSLZ4)@CSP72 [CX5001]  
LH28F640BFB(PB)@FBGA60 [CX5007]                    LH28F640BFB(PT)@FBGA60 [CX5007]  
LH28F640BFE(PB)@TSOP48 [CX1004]                    LH28F640BFE(PT)@TSOP48 [CX1004]  
LH28F640BFHB(PB)@FBGA60 [CX5007]                    LH28F640BFHB(PT)@FBGA60 [CX5007]  
LH28F640BFHBD@SSOP56 [CX0051]                    LH28F640BFHE(PB)@TSOP48 [CX1004]  
LH28F640BFHE(PBTL70A)@TSOP48 [CX1004]  
LH28F640BFHE(PT)@TSOP48 [CX1004]  
LH28F640BFHE(PTTL70A)@TSOP48 [CX1004]  
LH28F640BFHE(PTTLHIA)@TSOP48 [CX1004]  
LH28F640BFHG(PTTLZ6)@FBGA48 [CX5085]  
LH28F640BNHG(PBSL60)@CSP56 [CX5093]  
LH28F640BNHG(PTSL70)@CSP56 [CX5093]  
LH28F640SPHT@TSOP56 [CX1055]                    LH28F800BGB(B)@CSP48 [CX50UN]  
LH28F800BGB(T)@CSP48 [CX50UN]                    LH28F800BGE(B)@TSOP48 [CX1004]  
LH28F800BGE(T)@TSOP48 [CX1004]                    LH28F800BGHB(B)@CSP48 [CX50UN]  
LH28F800BGHB(T)@CSP48 [CX50UN]                    LH28F800BGHE(B)@TSOP48 [CX1004]

LH28F800BGHE(T)@TSOP48 [CX1004]  
LH28F800BGHE(TTL10)@TSOP48 [CX1004]  
LH28F800BGN(B)@PSOP44 [CX1014] LH28F800BGN(T)@PSOP44 [CX1014]  
LH28F800BH-B@TSOP48 [CX1004]  
LH28F800BJE(PB)(OTP)@TSOP48 [CX1004]  
LH28F800BJE(PB)@TSOP48 [CX1004]  
LH28F800BJE(PT)(OTP)@TSOP48 [CX1004]  
LH28F800BJE(PT)@TSOP48 [CX1004]  
LH28F800BJHE(PB)(OTP)@TSOP48 [CX1004]  
LH28F800BJHE(PT)(OTP)@TSOP48 [CX1004]  
LH28F800BJHG(PB)(OTP)@CSP48 [CX50UN]  
LH28F800BJR(PT)(OTP)@TSOP48 [CX1004]  
LH28F800BVB(B)@CSP48 [CX50UN] LH28F800BVB(T)@CSP48 [CX50UN]  
LH28F800BV-B@TSOP48 [CX1004] LH28F800BVE(B)@TSOP48 [CX1004]  
LH28F800BVE(T)@TSOP48 [CX1004]  
LH28F800BVE(TV85)@TSOP48 [CX1004]  
LH28F800BVHB(B)@CSP48 [CX50UN] LH28F800BVHB(T)@CSP48 [CX50UN]  
LH28F800BVHB@TSOP48 [CX1004] LH28F800BVHE(B)@TSOP48 [CX1004]  
LH28F800BVHE(T)@TSOP48 [CX1004] LH28F800BVHT@TSOP48 [CX1004]  
LH28F800BVN(B)@PSOP44 [CX1014] LH28F800BVN(T)@PSOP44 [CX1014]  
LH28F800BVN(TV85)@PSOP44 [CX1014]  
LH28F800BV-T@TSOP48 [CX1004] LH28F800SG(L100)@TSOP48 [CX1004]  
LH28F800SG(L120)@TSOP48 [CX1004] LH28F800SG(L70)@TSOP48 [CX1004]  
LH28F800SG(L80)@TSOP48 [CX1004] LH28F800SG(L85)@TSOP48 [CX1004]  
LH28F800SGH(L100)@TSOP48 [CX1004]  
LH28F800SGH(L120)@TSOP48 [CX1004]  
LH28F800SGH(L70)@TSOP48 [CX1004] LH28F800SGH(L80)@TSOP48 [CX1004]  
LH28F800SGH(L85)@TSOP48 [CX1004]  
LH28F800SGHE(L70)@TSOP48 [CX1004]  
LH28F800SUT@TSOP56 [CX1011] LHF00L03@PLCC32 [CX2032]  
LHF00L04@TSOP40 [CX1006] LHF00L06@TSOP40 [CX1006]  
LHF00L07@PLCC32 [CX2032]  
LHF00L08(LH28F320T)@FBGA48 [CX5002]  
LHF00L09(LH28F320B)@FBGA48 [CX5002]  
LHF00L10(LH28F320T)@FBGA48 [CX5080]  
LHF00L11(LH28F320B)@FBGA48 [CX5080]  
LHF00L12(LH28F320T)@TSOP48 [CX1004]  
LHF00L13(LH28F320B)@TSOP48 [CX1004]  
LHF00L14(LH28F320T)@TSOP48 [CX1004]  
LHF00L15(LH28F320B)@TSOP48 [CX1004]  
LHF00L24(LH28F160T)@FBGA48 [CX5002]  
LHF00L25(LH28F160B)@FBGA48 [CX5002]  
LHF00L28(LH28F160T)@TSOP48 [CX1004]  
LHF00L29(LH28F160B)@TSOP48 [CX1004]  
LHF00L30(LH28F160T)@TSOP48 [CX1004]  
LHF00L31(LH28F160B)@TSOP48 [CX1004]  
LRS1311@FBGA72 [CX5001] LRS1311A@FBGA72 [CX5001]  
LRS1315@FBGA72 [CX5001] LRS1315D@FBGA72 [CX5001]  
LRS1316@FBGA72 [CX5001] LRS1316A@FBGA72 [CX5001]  
LRS1317@FBGA72 [CX5001] LRS1320@FBGA72 [CX5001]  
LRS1320A@FBGA72 [CX5001] LRS1329@FBGA72 [CX5001]  
LRS1329A@FBGA72 [CX5001] LRS1330@FBGA72 [CX5001]  
LRS1330A@FBGA72 [CX5001] LRS1330B@FBGA72 [CX5001]  
LRS1330D@FBGA72 [CX5001] LRS1331@FBGA72 [CX5001]  
LRS1331B@FBGA72 [CX5001] LRS1331C@FBGA72 [CX5001]  
LRS1336@FBGA72 [CX5001] LRS1339@FBGA72 [CX5001]  
LRS1341@FBGA72 [CX5001] LRS1341A@FBGA72 [CX5001]  
LRS1342@FBGA72 [CX5001] LRS1342A@FBGA72 [CX5001]  
LRS1348@FBGA72 [CX5001] LRS1348B@FBGA72 [CX5001]



LRS1348E@FBGA72 [CX5001]  
LRS1356@FBGA72 [CX5001]  
LRS1360C@FBGA72 [CX5001]  
LRS1370B@FBGA72 [CX5001]  
LRS1381@FBGA72 [CX5001]  
LRS1383@FBGA72 [CX5001]  
LRS1383F@FBGA72 [CX5001]  
LRS1385@FBGA72 [CX5001]  
LRS1387@FBGA72 [CX5001]  
LRS1392A@FBGA72 [CX5001]  
LRS1393C@FBGA72 [CX5001]  
LRS1396@TSOP56 [CX1055]  
LRS13A1@FBGA72 [CX5001]  
LRS13A3@FBGA72 [CX5001]  
LRS13A5@FBGA72 [CX5001]  
LRS13A8@TSOP56 [CX1055]  
LRS1806A@FBGA72 [CX5001]  
LRS1806F@FBGA72 [CX5001]  
LRS1807A@FBGA72 [CX5001]  
LRS1808A@FBGA72 [CX5001]  
LRS1811A@FBGA72 [CX5001]  
LRS1815@FBGA72 [CX5001]  
LRS1816A@FBGA72 [CX5001]  
LRS1822@FBGA72 [CX5001]  
LRS1826@FBGA72 [CX5001]  
LRS1827@FBGA72 [CX5001]  
LRS1828B@FBGA72 [CX5001]  
LRS1829@FBGA72 [CX5001]  
LRS1834@FBGA72 [CX5001]  
LRS1845@FBGA72 [CX5001]  
LRS1851@FBGA72 [CX5001]  
LRS1853@FBGA72 [CX5001]  
LRS18621@FBGA72 [CX5001]  
LRS1864@FBGA72 [CX5001]  
LRS1864A@FBGA72 [CX5001]  
LRS18712@FBGA72 [CX5001]  
LRS1872@FBGA72 [CX5001]  
LRS1872A@FBGA72 [CX5001]  
LRS1875@FBGA72 [CX5001]  
LRS1876@FBGA72 [CX5001]  
LRS1876A@FBGA72 [CX5001]  
LRS18811@FBGA72 [CX5001]  
LRS18831@FBGA72 [CX5001]  
LRS1890@FBGA72 [CX5001]  
LRS1892@FBGA72 [CX5001]  
LRS1896@FBGA72 [CX5001]  
LRS1898@FBGA72 [CX5001]  
LRS18A2@FBGA72 [CX50UN]  
LRS18A4@FBGA72 [CX50UN]  
LRS18A8@FBGA88 [CX50UN]  
LRS18AA@FBGA88 [CX50UN]  
LRS18AC@FBGA88 [CX50UN]  
LRS18AE@FBGA88 [CX50UN]  
LRS18AG@FBGA88 [CX50UN]  
LRS18AJ@FBGA88 [CX50UN]  
LRS18AL@FBGA72 [CX50UN]  
LRS18AN@FBGA88 [CX50UN]  
LRS18AT@FBGA88 [CX50UN]  
LRS18AV@FBGA88 [CX50UN]  
LRS1350@FBGA72 [CX5001]  
LRS1360@FBGA72 [CX5001]  
LRS1370@FBGA72 [CX5001]  
LRS1380@FBGA72 [CX5001]  
LRS1382@FBGA72 [CX5001]  
LRS1383C@FBGA72 [CX5001]  
LRS1384@FBGA72 [CX5001]  
LRS1386@FBGA72 [CX5001]  
LRS1391@FBGA72 [CX5001]  
LRS1393A@FBGA72 [CX5001]  
LRS1395@FBGA72 [CX5001]  
LRS13A0@FBGA72 [CX5001]  
LRS13A2@FBGA72 [CX5001]  
LRS13A4@FBGA72 [CX5001]  
LRS13A6@FBGA72 [CX5001]  
LRS1805A@FBGA72 [CX5001]  
LRS1806C@FBGA72 [CX5001]  
LRS1806J@FBGA72 [CX5001]  
LRS1808@FBGA72 [CX5001]  
LRS1811@FBGA72 [CX5001]  
LRS1812@FBGA72 [CX5001]  
LRS1816@FBGA72 [CX5001]  
LRS1821@FBGA72 [CX5001]  
LRS1825@FBGA72 [CX5001]  
LRS1826A@FBGA72 [CX5001]  
LRS1828@FBGA72 [CX5001]  
LRS1828C@FBGA72 [CX5001]  
LRS1832@FBGA72 [CX5001]  
LRS1844@FBGA72 [CX5001]  
LRS1850@FBGA72 [CX5001]  
LRS1852@FBGA72 [CX5001]  
LRS1857@FBGA72 [CX5001]  
LRS1862E@FBGA72 [CX5001]  
LRS18641@FBGA72 [CX5001]  
LRS1871@FBGA72 [CX5001]  
LRS1871A@FBGA72 [CX5001]  
LRS18722@FBGA72 [CX5001]  
LRS1874@FBGA72 [CX5001]  
LRS18751@FBGA72 [CX5001]  
LRS18761@FBGA72 [CX5001]  
LRS18791@FBGA72 [CX5001]  
LRS18821@FBGA72 [CX5001]  
LRS18841@FBGA72 [CX5001]  
LRS1891@FBGA72 [CX5001]  
LRS18941@FBGA72 [CX5001]  
LRS1897@FBGA72 [CX5001]  
LRS18A1@FBGA72 [CX50UN]  
LRS18A3@FBGA72 [CX50UN]  
LRS18A7@FBGA88 [CX50UN]  
LRS18A9@FBGA88 [CX50UN]  
LRS18AB@FBGA88 [CX50UN]  
LRS18AD@FBGA88 [CX50UN]  
LRS18AF@FBGA88 [CX50UN]  
LRS18AH@FBGA88 [CX50UN]  
LRS18AK@FBGA72 [CX50UN]  
LRS18AM@FBGA88 [CX50UN]  
LRS18AS@FBGA88 [CX50UN]  
LRS18AU@FBGA88 [CX50UN]  
LRS18AW@FBGA88 [CX50UN]

LRS18AY@FBGA88 [CX50UN]  
LRS18B0@FBGA72 [CX5001]  
LRS18B2@FBGA88 [CX5001]  
LRS18B5@FBGA88 [CX5001]  
LRS18B7@FBGA88 [CX5001]  
LRS18B9@FBGA88 [CX5001]  
LRS18BF@FBGA88 [CX5001]  
LRS18BH@FBGA88 [CX5001]  
LRS18BL@FBGA88 [CX5001]  
LRS18BN@FBGA88 [CX5001]  
LRS18BT@FBGA72 [CX5001]  
LRS18C8A@FBGA72 [CX5001]  
LRS1B02@FBGA72 [CX5001]  
LRS1B05@FBGA72 [CX5001]  
LRS1B07@FBGA72 [CX5001]  
LRS1B30@FBGA72 [CX5001]

LRS18AZ@FBGA88 [CX50UN]  
LRS18B1@FBGA88 [CX5001]  
LRS18B4@FBGA88 [CX5001]  
LRS18B6@FBGA88 [CX5001]  
LRS18B8@FBGA88 [CX5001]  
LRS18BE@FBGA88 [CX5001]  
LRS18BG@FBGA88 [CX5001]  
LRS18BK@FBGA88 [CX5001]  
LRS18BM@FBGA88 [CX5001]  
LRS18BS@FBGA72 [CX5001]  
LRS18BU@FBGA88 [CX5001]  
LRS18C8G@FBGA72 [CX5001]  
LRS1B04@FBGA72 [CX5001]  
LRS1B06@FBGA72 [CX5001]  
LRS1B12@FBGA72 [CX5001]

## SIEMENS

### E ( E ) PROM / FRAM / NVRAM

SDA2526 [CX0001]  
SDA2546 [CX0001]  
SDA25X26 [CX0001]  
SDA25X46 [CX0001]  
SDE2526 [CX0001]  
SDE2546 [CX0001]  
SDE25X26 [CX0001]  
SDE25X46 [CX0001]  
SLA24C01 [CX0001]  
SLA24C02 [CX0001]  
SLA24C04 [CX0001]  
SLA24C08 [CX0001]  
SLA24C16 [CX0001]  
SLA24C164 [CX0001]  
SLA24C32 [CX0001]  
SLA24C64 [CX0001]  
SLA25010 [CX0001]  
SLA25020 [CX0001]  
SLA25040 [CX0001]  
SLA25080 [CX0001]  
SLA25160 [CX0001]  
SLE24C01 [CX0001]  
SLE24C02 [CX0001]  
SLE24C04 [CX0001]  
SLE24C08 [CX0001]  
SLE24C16 [CX0001]  
SLE24C164 [CX0001]  
SLE24C32 [CX0001]  
SLE24C64 [CX0001]  
SLE25010 [CX0001]  
SLE25020 [CX0001]  
SLE25040 [CX0001]  
SLE25080 [CX0001]  
SLE25160 [CX0001]

SDA2526@SOIC8 [CX1045]  
SDA2546@SOIC8 [CX1045]  
SDA25X26@SOIC8 [CX1045]  
SDA25X46@SOIC8 [CX1045]  
SDE2526@SOIC8 [CX1045]  
SDE2546@SOIC8 [CX1045]  
SDE25X26@SOIC8 [CX1045]  
SDE25X46@SOIC8 [CX1045]  
SLA24C01@SOIC8 [CX1045]  
SLA24C02@SOIC8 [CX1045]  
SLA24C04@SOIC8 [CX1045]  
SLA24C08@SOIC8 [CX1045]  
SLA24C16@SOIC8 [CX1045]  
SLA24C164@SOIC8 [CX1045]  
SLA24C32@SOIC8 [CX1045]  
SLA24C64@SOIC8 [CX1045]  
SLA25010@SOIC8 [CX1045]  
SLA25020@SOIC8 [CX1045]  
SLA25040@SOIC8 [CX1045]  
SLA25080@SOIC8 [CX1045]  
SLA25160@SOIC8 [CX1045]  
SLE24C01@SOIC8 [CX1045]  
SLE24C02@SOIC8 [CX1045]  
SLE24C04@SOIC8 [CX1045]  
SLE24C08@SOIC8 [CX1045]  
SLE24C16@SOIC8 [CX1045]  
SLE24C164@SOIC8 [CX1045]  
SLE24C32@SOIC8 [CX1045]  
SLE24C64@SOIC8 [CX1045]  
SLE25010@SOIC8 [CX1045]  
SLE25020@SOIC8 [CX1045]  
SLE25040@SOIC8 [CX1045]  
SLE25080@SOIC8 [CX1045]  
SLE25160@SOIC8 [CX1045]

### MICROCONTROLLER

SAB-C501G-1E [CX0001]	SAB-C501G-1E@PLCC44 [CX2044]
SAB-C501G-1E@TQFP44 [CX3002]	SAB-C504-2EM@TQFP44 [CX3002]
SAB-C505A-4EM@TQFP44 [CX3002]	SAB-C505CA-4EM@TQFP44 [CX3002]
SAB-C505L-4EM@PQFP80 [CX3018]	SAB-C508-4EM@TQFP64 [CX3014]
SAB-C508-4EP@SDIP64 [CX0064]	SAB-C515C-8EM@TQFP80 [CX3018]
SAB-C540U-1EN@PLCC44 [CX2044]	SAB-C540U-1EP@SDIP52 [CX0052]
SAB-C541U-1EN@PLCC44 [CX2044]	SAB-C541U-1EP@SDIP52 [CX0052]
SAF-C501G-1EN@PLCC44 [CX2044]	SAF-C501G-1EP [CX0001]
SAF-C504-2EM@TQFP44 [CX3002]	SAF-C505A-4EM@TQFP44 [CX3002]
SAF-C505CA-4EM@TQFP44 [CX3002]	SAF-C505L-4EM@PQFP80 [CX3018]
SAF-C508-4EM@TQFP64 [CX3014]	SAF-C508-4EP@SDIP64 [CX0064]
SAF-C513AO-2EM@TQFP44 [CX3002]	SAF-C513AO-2EN@PLCC44 [CX2044]
SAF-C513AO-2EP [CX0001]	SAF-C515C-8EM@TQFP80 [CX3018]
SAF-XC822-1FRI@TSSOP16 [CX1000]	SAF-XC822M-1FRI@TSSOP16 [CX1000]
SAF-XC822MT-1FRI@TSSOP16 [CX1000]	SAF-XC822T-1FRI@TSSOP16 [CX1000]
SAF-XC822T-0FRI@TSSOP16 [CX1000]	SAF-XC824MT-1FGI@SOIC20 [CX1033]
SAF-XC824M-1FGI@SOIC20 [CX1033]	SAF-XC836-2FRI@TSSOP28 [CX1001]
SAF-XC835MT-2FGI@SOIC24 [CX1033]	SAF-XC836M-2FRI@TSSOP28 [CX1001]
SAF-XC836M-1FRI@TSSOP28 [CX1001]	SAF-XC836MT-2FRA@TSSOP28 [CX1001]
SAF-XC836MT-2FRA@TSSOP28 [CX1001]	SAF-XC836MT-2FRI@TSSOP28 [CX1001]
SAF-XC836MT-2FRI@TSSOP28 [CX1001]	SAF-XC836T-2FRI@TSSOP28 [CX1001]
SAF-XC856CLM-13FFI@QFP64 [CX3011]	SAF-XC856LM-13FFI@QFP64 [CX3011]
SAF-XC856CLM-16FFI@QFP64 [CX3011]	SAF-XC856LM-9FFI@QFP64 [CX3011]
SAF-XC856CLM-9FFI@QFP64 [CX3011]	SAF-XC856LM-16FFI@QFP64 [CX3011]
SAF-XC856LM-16FFI@QFP64 [CX3011]	SAF-XC858CA-13FFI(5v)QFP64 [CX3011]
SAF-XC858CA-13FFI(5v)QFP64 [CX3011]	SAF-XC858CA-16FFI(5v)QFP64 [CX3011]
SAF-XC858CA-9FFI(5v)QFP64 [CX3011]	SAF-XC878-13FFI(3.3v)@QFP64 [CX3011]
SAF-XC878-13FFI(3.3v)@QFP64 [CX3011]	SAF-XC878-13FFI(5v)@QFP64 [CX3011]
SAF-XC878-13FFI(5v)@QFP64 [CX3011]	SAF-XC878-16FFI(3.3v)@QFP64 [CX3011]
SAF-XC878-16FFI(3.3v)@QFP64 [CX3011]	SAF-XC878-16FFI(5v)@QFP64 [CX3011]
SAF-XC878-16FFI(5v)@QFP64 [CX3011]	SAF-XC878CM-13FFI(3.3v)@QFP64 [CX3011]
SAF-XC878CM-13FFI(3.3v)@QFP64 [CX3011]	SAF-XC878CM-13FFI(5v)@QFP64 [CX3011]
SAF-XC878CM-16FFI(3.3v)@QFP64 [CX3011]	SAF-XC878CM-16FFI(3.3v)@QFP64 [CX3011]
SAF-XC878CM-16FFI(5v)@QFP64 [CX3011]	SAF-XC878CM-16FFI(5v)@QFP64 [CX3011]
SAF-XC878M-13FFI(3.3v)@QFP64 [CX3011]	SAF-XC878M-13FFI(5v)@QFP64 [CX3011]
SAF-XC878M-13FFI(5v)@QFP64 [CX3011]	SAF-XC878M-16FFI(3.3v)@QFP64 [CX3011]
SAF-XC878M-16FFI(3.3v)@QFP64 [CX3011]	SAF-XC878M-16FFI(5v)@QFP64 [CX3011]
SAF-XC878M-16FFI(5v)@QFP64 [CX3011]	SAF-XC886-6FFA(3.3v)@QFP48 [CX3007]
SAF-XC886-6FFA(3.3v)@QFP48 [CX3007]	SAF-XC886-6FFA(5v)@QFP48 [CX3007]
SAF-XC886-6FFA(5v)@QFP48 [CX3007]	SAF-XC886-6FFI(3.3v)@QFP48 [CX3007]
SAF-XC886-6FFI(3.3v)@QFP48 [CX3007]	SAF-XC886-6FFI(5v)@QFP48 [CX3007]
SAF-XC886-6FFI(5v)@QFP48 [CX3007]	SAF-XC886-8FFA(3.3v)@QFP48 [CX3007]
SAF-XC886-8FFA(3.3v)@QFP48 [CX3007]	SAF-XC886-8FFA(5v)@QFP48 [CX3007]
SAF-XC886-8FFA(5v)@QFP48 [CX3007]	SAF-XC886-8FFI(3.3v)@QFP48 [CX3007]
SAF-XC886-8FFI(3.3v)@QFP48 [CX3007]	SAF-XC886-8FFI(5v)@QFP48 [CX3007]
SAF-XC886-8FFI(5v)@QFP48 [CX3007]	SAF-XC886C-6FFA(3.3v)@QFP48 [CX3007]
SAF-XC886C-6FFA(3.3v)@QFP48 [CX3007]	SAF-XC886C-6FFA(5v)@QFP48 [CX3007]
SAF-XC886C-6FFA(5v)@QFP48 [CX3007]	SAF-XC886C-6FFI(3.3v)@QFP48 [CX3007]
SAF-XC886C-6FFI(3.3v)@QFP48 [CX3007]	SAF-XC886C-6FFI(5v)@QFP48 [CX3007]
SAF-XC886C-6FFI(5v)@QFP48 [CX3007]	SAF-XC886C-8FFA(3.3v)@QFP48 [CX3007]
SAF-XC886C-8FFA(3.3v)@QFP48 [CX3007]	SAF-XC886C-8FFA(5v)@QFP48 [CX3007]
SAF-XC886C-8FFA(5v)@QFP48 [CX3007]	SAF-XC886C-8FFI(3.3v)@QFP48 [CX3007]
SAF-XC886C-8FFI(3.3v)@QFP48 [CX3007]	SAF-XC886C-8FFI(5v)@QFP48 [CX3007]
SAF-XC886C-8FFI(5v)@QFP48 [CX3007]	SAF-XC886CLM-6FFA(3.3v)@QFP48 [CX3007]
SAF-XC886CLM-6FFA(3.3v)@QFP48 [CX3007]	SAF-XC886CLM-6FFA(5v)@QFP48 [CX3007]

SAF-XC886CLM-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CLM-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CLM-8FFI(5v)@QFP48 [CX3007]  
SAF-XC886CM-6FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-6FFA(5v)@QFP48 [CX3007]  
SAF-XC886CM-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886CM-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886CM-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886CM-8FFI(5v)@QFP48 [CX3007]  
SAF-XC886LM-6FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-6FFA(5v)@QFP48 [CX3007]  
SAF-XC886LM-6FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-6FFI(5v)@QFP48 [CX3007]  
SAF-XC886LM-8FFA(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-8FFA(5v)@QFP48 [CX3007]  
SAF-XC886LM-8FFI(3.3v)@QFP48 [CX3007]  
SAF-XC886LM-8FFI(5v)@QFP48 [CX3007]  
SAF-XC888-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888C-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888C-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888C-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888C-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888C-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888C-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888C-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888C-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CLM-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888CM-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888CM-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888CM-8FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888CM-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888CM-8FFI(5v)@QFP64 [CX3011]  
SAF-XC888LM-6FFA(3.3v)@QFP64 [CX3011]  
SAF-XC888LM-6FFA(5v)@QFP64 [CX3011]  
SAF-XC888LM-6FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888LM-6FFI(5v)@QFP64 [CX3011]  
SAF-XC888LM-8FFA(3.3v)@QFP64 [CX3011]

SAF-XC888LM-8FFA(5v)@QFP64 [CX3011]  
SAF-XC888LM-8FFI(3.3v)@QFP64 [CX3011]  
SAF-XC888LM-8FFI(5v)@QFP64 [CX3011]  
SAH-C504-2EM@TQFP44 [CX3002]                   SAH-C505A-4EM@TQFP44 [CX3002]  
SAH-C505CA-4EM@TQFP44 [CX3002]               SAK-C504-2EM@TQFP44 [CX3002]  
SAK-C505A-4EM@TQFP44 [CX3002]               SAK-C505CA-4EM@TQFP44 [CX3002]  
SAK-C505L-4EM@PQFP80 [CX3018]               SAK-C515C-8EM@TQFP80 [CX3018]  
SAK-XC824M-1FGI@SOIC20 [CX1033]  
SAK-XC886-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886C-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886C-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886C-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886C-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886C-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886C-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886C-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886C-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CLM-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886CM-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886CM-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886CM-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886CM-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886CM-8FFI(5v)@QFP48 [CX3007]  
SAK-XC886LM-6FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-6FFA(5v)@QFP48 [CX3007]  
SAK-XC886LM-6FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-6FFI(5v)@QFP48 [CX3007]  
SAK-XC886LM-8FFA(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-8FFA(5v)@QFP48 [CX3007]  
SAK-XC886LM-8FFI(3.3v)@QFP48 [CX3007]  
SAK-XC886LM-8FFI(5v)@QFP48 [CX3007]  
SAK-XC888-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888C-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888C-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888C-6FFI(3.3v)@QFP64 [CX3011]

SAK-XC888C-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888C-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888C-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888C-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888C-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CLM-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888CM-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888CM-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888CM-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888CM-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888CM-8FFI(5v)@QFP64 [CX3011]  
SAK-XC888LM-6FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-6FFA(5v)@QFP64 [CX3011]  
SAK-XC888LM-6FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-6FFI(5v)@QFP64 [CX3011]  
SAK-XC888LM-8FFA(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-8FFA(5v)@QFP64 [CX3011]  
SAK-XC888LM-8FFI(3.3v)@QFP64 [CX3011]  
SAK-XC888LM-8FFI(5v)@QFP64 [CX3011]  
SAX-XC878-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878-16FFA(5v)@QFP64 [CX3011]  
SAX-XC878C-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878C-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878C-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878C-16FFA(5v)@QFP64 [CX3011]  
SAX-XC878CM-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878CM-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878CM-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878CM-16FFA(5v)@QFP64 [CX3011]  
SAX-XC878L-13FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878L-13FFA(5v)@QFP64 [CX3011]  
SAX-XC878L-16FFA(3.3v)@QFP64 [CX3011]  
SAX-XC878L-16FFA(5v)@QFP64 [CX3011]

## SIERRA

### E (E) PROM/FRAM/NVRAM

SC22101CM [CX1033]                      SC22101CN [CX0001]  
SC22201CM [CX1033]                      SC22201CN [CX0001]

## SIGNETICS

### E (E) PROM/FRAM/NVRAM

27C010 [CX0001]	27C010@PLCC32 [CX2032]
27C010@TSOP32 [CX1002]	27C040 [CX0001]
27C040@PLCC32 [CX2032]	27C040@TSOP32 [CX1002]
27C210 [CX0001]	27C210@PLCC44 [CX2044]
27C240 [CX0001]	27C240@PLCC44 [CX2044]
27C256 [CX0001]	27C256@PLCC32 [CX2032]
27C512 [CX0001]	27C512@PLCC32 [CX2032]
27C64A [CX0001]	27C64A@PLCC32 [CX2032]
27HC641 [CX0001]	27HC641@PLCC28 [CX2028]
27HC642 [CX0001]	27HC642@PLCC28 [CX2028]
PCA8582A [CX0001]	PCA8582A@SOIC8 [CX1045]
PCA8582B [CX0001]	PCA8582B@SOIC8 [CX1045]
PCA8582C [CX0001]	PCA8582C@SOIC8 [CX1045]
PCA8582D [CX0001]	PCA8582D@SOIC8 [CX1045]
PCA8582E [CX0001]	PCA8582E@SOIC8 [CX1045]
PCD8582A [CX0001]	PCD8582A@SOIC8 [CX1045]
PCD8582B [CX0001]	PCD8582B@SOIC8 [CX1045]
PCD8582C [CX0001]	PCD8582C@SOIC8 [CX1045]
PCD8582D [CX0001]	PCD8582D@SOIC8 [CX1045]
PCD8582E [CX0001]	PCD8582E@SOIC8 [CX1045]
PCF8582A [CX0001]	PCF8582A@SOIC8 [CX1045]
PCF8582B [CX0001]	PCF8582B@SOIC8 [CX1045]
PCF8582C [CX0001]	PCF8582C@SOIC8 [CX1045]
PCF8582D [CX0001]	PCF8582D@SOIC8 [CX1045]
PCF8582E [CX0001]	PCF8582E@SOIC8 [CX1045]
PCF8594 [CX0001]	PCF8594@SOIC8 [CX1045]
PCF8594C [CX0001]	PCF8594C@SOIC8 [CX1045]
PCF8594D [CX0001]	PCF8594D@SOIC8 [CX1045]
PCF8594E [CX0001]	PCF8594E@SOIC8 [CX1045]
PCF8598 [CX0001]	PCF8598@SOIC8 [CX1044]
PCF8598C [CX0001]	PCF8598C@SOIC8 [CX1044]
PCF8598D [CX0001]	PCF8598D@SOIC8 [CX1044]
PCF8598E [CX0001]	PCF8598E@SOIC8 [CX1044]

## BPROM

82LS135 [CX0001]	82LS135@PLCC20 [CX2020]
82S123 [CX0001]	82S123A [CX0001]
82S126 [CX0001]	82S126A [CX0001]
82S129 [CX0001]	82S129A [CX0001]
82S130 [CX0001]	82S130A [CX0001]
82S131 [CX0001]	82S131A [CX0001]
82S135 [CX0001]	82S135@PLCC20 [CX2020]
82S136 [CX0001]	82S137 [CX0001]
82S137A [CX0001]	82S137B [CX0001]
82S137C [CX0001]	82S140 [CX0001]
82S141 [CX0001]	82S146 [CX0001]
82S146@PLCC20 [CX2020]	82S147 [CX0001]
82S147@PLCC20 [CX2020]	82S147A [CX0001]
82S147A@PLCC20 [CX2020]	82S147B [CX0001]
82S147B@PLCC20 [CX2020]	82S167 [CX0001]
82S23 [CX0001]	82S23A [CX0001]

## PLD

82S105 [CX0001]	82S105@PLCC28 [CX2028]
82S152 [CX0001]	82S152@PLCC20 [CX2020]
82S153 [CX0001]	82S153@PLCC20 [CX2020]

82S155 [CX0001]	82S155@PLCC20 [CX2020]
82S157 [CX0001]	82S157@PLCC20 [CX2020]
82S159 [CX0001]	82S159@PLCC20 [CX2020]
82S167 [CX0001]	82S167@PLCC28 [CX2028]
82S168 [CX0001]	82S168@PLCC28 [CX2028]
82S173 [CX0001]	82S173@PLCC28 [CX2028]
82S179 [CX0001]	82S179@PLCC28 [CX2028]
PLS104 [CX0001]	PLS104@PLCC28 [CX2028]
PLS104A [CX0001]	PLS104A@PLCC28 [CX2028]
PLS105 [CX0001]	PLS105@PLCC28 [CX2028]
PLS105A [CX0001]	PLS105A@PLCC28 [CX2028]
PLS152 [CX0001]	PLS152@PLCC20 [CX2020]
PLS153 [CX0001]	PLS153@PLCC20 [CX2020]
PLS153A [CX0001]	PLS153A@PLCC20 [CX2020]
PLS155 [CX0001]	PLS155@PLCC20 [CX2020]
PLS157 [CX0001]	PLS157@PLCC20 [CX2020]
PLS159 [CX0001]	PLS159@PLCC20 [CX2020]
PLS159A [CX0001]	PLS159A@PLCC20 [CX0001]
PLS167 [CX0001]	PLS167@PLCC28 [CX2028]
PLS167A [CX0001]	PLS167A@PLCC28 [CX2028]
PLS168 [CX0001]	PLS168@PLCC28 [CX2028]
PLS168A [CX0001]	PLS168A@PLCC28 [CX2028]
PLS173 [CX0001]	PLS173@PLCC28 [CX2028]
PLS179 [CX0001]	PLS179@PLCC28 [CX2028]

#### MICROCONTROLLER

PSD301@PLCC44 [CX2044]	PSD301L@PLCC44 [CX2044]
PSD302@PLCC44 [CX2044]	PSD302L@PLCC44 [CX2044]
PSD303@PLCC44 [CX2044]	PSD303L@PLCC44 [CX2044]
PSD311@PLCC44 [CX2044]	PSD311L@PLCC44 [CX2044]
PSD312@PLCC44 [CX2044]	PSD312L@PLCC44 [CX2044]
PSD313@PLCC44 [CX2044]	PSD313@TQFP44 [CX3003]
PSD313-B@PLCC44 [CX2044]	PSD313-B@TQFP44 [CX3003]
PSD313L@PLCC44 [CX2044]	PSD313L@TQFP44 [CX3003]
S87C054@SDIP42 [CX0042]	S87C055@SDIP42 [CX0042]
S87C51 [CX0001]	S87C51@PLCC44 [CX2044]
S87C51@TQFP44 [CX3002]	S87C51FA [CX0001]
S87C51FA@PLCC44 [CX2044]	S87C51FA@TQFP44 [CX3002]
S87C51FB [CX0001]	S87C51FB@PLCC44 [CX2044]
S87C51FB@TQFP44 [CX3002]	S87C51FC [CX0001]
S87C51FC@PLCC44 [CX2044]	S87C51FC@TQFP44 [CX3003]
S87C52 [CX0001]	S87C52@PLCC44 [CX2044]
S87C52@TQFP44 [CX3002]	S87C524 [CX0001]
S87C524@PLCC44 [CX2044]	S87C524@TQFP44 [CX3003]
S87C528 [CX0001]	S87C528@PLCC44 [CX2044]
S87C528@TQFP44 [CX3003]	S87C54 [CX0001]
S87C54@PLCC44 [CX2044]	S87C54@TQFP44 [CX3002]
S87C550 [CX0001]	S87C550@PLCC44 [CX2044]
S87C575 [CX0001]	S87C575@PLCC44 [CX2044]
S87C575@TQFP44 [CX3002]	S87C576 [CX0001]
S87C576@PLCC44 [CX2044]	S87C576@TQFP44 [CX3002]
S87C58 [CX0001]	S87C58@PLCC44 [CX2044]
S87C58@TQFP44 [CX3002]	S87C591@PLCC44 [CX2044]
S87C591@TQFP44 [CX3002]	S87C652 [CX0001]
S87C652@PLCC44 [CX2044]	S87C652@TQFP44 [CX3002]
S87C654 [CX0001]	S87C654@PLCC44 [CX2044]
S87C654@TQFP44 [CX3002]	S87C748 [CX0001]
S87C748@PLCC28 [CX2028]	S87C749 [CX0001]



S87C749@PLCC28 [CX2028]  
S87C750@PLCC28 [CX2028]  
S87C751 [CX0001]  
S87C751@SSOP24 [CX1026]  
S87C752@PLCC28 [CX2028]  
S87C754 [CX0001]  
S87C754@SSOP28 [CX1026]  
S87L51FA@PLCC44 [CX2044]  
S87L51FB [CX0001]  
S87L51FB@TQFP44 [CX3002]

S87C750 [CX0001]  
S87C750@SSOP24 [CX1026]  
S87C751@PLCC28 [CX2028]  
S87C752 [CX0001]  
S87C752@SSOP28 [CX1026]  
S87C754@PLCC28 [CX2028]  
S87L51FA [CX0001]  
S87L51FA@TQFP44 [CX3002]  
S87L51FB@PLCC44 [CX2044]

## Silicon Laboratories

### MICROCONTROLLER

C8051F000@TQFP64 [CX3011]  
C8051F002@TQFP32 [CX3001]  
C8051F006@TQFP48 [CX3007]  
C8051F010@TQFP64 [CX3011]  
C8051F012@TQFP32 [CX3001]  
C8051F016@TQFP48 [CX3007]  
C8051F018@TQFP64  
C8051F020@TQFP100 [CX3021]  
C8051F021@TQFP64 [CX3011]  
C8051F022@TQFP100 [CX3021]  
C8051F023@TQFP64 [CX3011]  
C8051F040@TQFP100 [CX3021]  
C8051F041@TQFP64 [CX3011]  
C8051F042@TQFP100 [CX3021]  
C8051F043@TQFP64 [CX3011]  
C8051F044@TQFP100 [CX3021]  
C8051F045@TQFP64 [CX3011]  
C8051F046@TQFP100 [CX3021]  
C8051F047@TQFP64 [CX3011]  
C8051F060@TQFP100 [CX3021]  
C8051F062@TQFP100 [CX3021]  
C8051F064@TQFP100 [CX3021]  
C8051F066@TQFP100 [CX3021]  
C8051F120\*ISP [CX0001]  
C8051F120-GQ\*ISP [CX0001]  
C8051F121\*ISP [CX0001]  
C8051F121-GQ\*ISP [CX0001]  
C8051F122\*ISP [CX0001]  
C8051F122-GQ\*ISP [CX0001]  
C8051F123\*ISP [CX0001]  
C8051F123-GQ\*ISP [CX0001]  
C8051F124\*ISP [CX0001]  
C8051F124-GQ\*ISP [CX0001]  
C8051F125\*ISP [CX0001]  
C8051F125-GQ\*ISP [CX0001]  
C8051F126\*ISP [CX0001]  
C8051F126-GQ\*ISP [CX0001]  
C8051F127\*ISP [CX0001]  
C8051F127-GQ\*ISP [CX0001]  
C8051F130\*ISP [CX0001]  
C8051F130-GQ\*ISP [CX0001]  
C8051F131\*ISP [CX0001]  
C8051F131-GQ\*ISP [CX0001]

C8051F001@TQFP48 [CX3007]  
C8051F005@TQFP64 [CX3011]  
C8051F007@TQFP32 [CX3001]  
C8051F011@TQFP48 [CX3007]  
C8051F015@TQFP64 [CX3011]  
C8051F017@TQFP32 [CX3001]  
C8051F019@TQFP48  
C8051F020JTAG [CX0001]  
C8051F021JTAG [CX0001]  
C8051F022JTAG [CX0001]  
C8051F023JTAG [CX0001]  
C8051F040JTAG [CX0001]  
C8051F041JTAG [CX0001]  
C8051F042JTAG [CX0001]  
C8051F043JTAG [CX0001]  
C8051F044JTAG [CX0001]  
C8051F045JTAG [CX0001]  
C8051F046JTAG [CX0001]  
C8051F047JTAG [CX0001]  
C8051F061@TQFP64 [CX3011]  
C8051F063@TQFP64 [CX3011]  
C8051F065@TQFP64 [CX3011]  
C8051F067@TQFP64 [CX3011]  
C8051F120@TQFP100 [CX3021]  
C8051F120-GQ@TQFP100 [CX3021]  
C8051F121@TQFP64 [CX3011]  
C8051F121-GQ@TQFP64 [CX3011]  
C8051F122@TQFP100 [CX3021]  
C8051F122-GQ@TQFP100 [CX3021]  
C8051F123@TQFP64 [CX3011]  
C8051F123-GQ@TQFP64 [CX3011]  
C8051F124@TQFP100 [CX3021]  
C8051F124-GQ@TQFP100 [CX3021]  
C8051F125@TQFP64 [CX3011]  
C8051F125-GQ@TQFP64 [CX3011]  
C8051F126@TQFP100 [CX3021]  
C8051F126-GQ@TQFP100 [CX3021]  
C8051F127@TQFP64 [CX3011]  
C8051F127-GQ@TQFP64 [CX3011]  
C8051F130@TQFP100 [CX3021]  
C8051F130-GQ@TQFP100 [CX3021]  
C8051F131@TQFP64 [CX3011]  
C8051F131-GQ@TQFP64 [CX3011]

C8051F132\*ISP [CX0001] C8051F132@TQFP100 [CX3021]  
C8051F132-GQ\*ISP [CX0001] C8051F132-GQ@TQFP100 [CX3021]  
C8051F133\*ISP [CX0001] C8051F133@TQFP64 [CX3011]  
C8051F133-GQ\*ISP [CX0001] C8051F133-GQ@TQFP64 [CX3011]  
C8051F206@TQFP48 [CX3007] C8051F220@TQFP48 [CX3007]  
C8051F221@TQFP32 [CX3001] C8051F226@TQFP48 [CX3007]  
C8051F230@TQFP48 [CX3007] C8051F231@TQFP32 [CX3001]  
C8051F236@TQFP48 [CX3007] C8051F300@QFN11 [CX4007]  
C8051F300-GM@QFN11 [CX4007] C8051F300-GS [CX1016]  
C8051F301@QFN11 [CX4007] C8051F301-GM@QFN11 [CX4007]  
C8051F301-GS@SOIC14 [CX1016] C8051F302@QFN11 [CX4007]  
C8051F302-GM@QFN11 [CX4007] C8051F302-GS [CX1016]  
C8051F303@QFN11 [CX4007] C8051F303-GM@QFN11 [CX4007]  
C8051F303-GS [CX1016] C8051F304@QFN11 [CX4007]  
C8051F304-GM@QFN11 [CX4007] C8051F304-GS [CX1016]  
C8051F305@QFN11 [CX4007] C8051F305-GM@QFN11 [CX4007]  
C8051F305-GS [CX1016] C8051F310@TQFP32 [CX3001]  
C8051F310A@TQFP32 [CX3001] C8051F310A-GQ@TQFP32 [CX3001]  
C8051F310-GQ@TQFP32 [CX3001] C8051F311@QFN28 [CX4013]  
C8051F311-GM@QFN28 [CX4013] C8051F312@TQFP32 [CX3001]  
C8051F312-GQ@TQFP32 [CX3001] C8051F313@QFN28 [CX4013]  
C8051F313-GM@QFN28 [CX4013] C8051F314@TQFP32 [CX3001]  
C8051F314-GQ@TQFP32 [CX3001] C8051F315@QFN28 [CX4013]  
C8051F315-GM@QFN28 [CX4013] C8051F316-GM@QFN24 [CX4012]  
C8051F317-GM@QFN24 [CX4012] C8051F320@TQFP32 [CX3001]  
C8051F320A@TQFP32 [CX3001] C8051F320A-GQ@TQFP32 [CX3001]  
C8051F320-GQ@TQFP32 [CX3001] C8051F321@QFN28 [CX4013]  
C8051F321@QFN28(Left Down) [CX4013] C8051F321A@QFN28 [CX4013]  
C8051F321A@QFN28(Left Down) [CX4013] C8051F321A-GM@QFN28 [CX4013]  
C8051F321A-GM@QFN28(Left Down) [CX4013] C8051F321-GM@QFN28 [CX4013]  
C8051F321-GM@QFN28(Left Down) [CX4013] C8051F326@QFN28 [CX4013]  
C8051F326-GM@QFN28 [CX4013] C8051F326-GM@QFN28 [CX4013]  
C8051F326-GQ@QFN28 [CX4013] C8051F327@QFN28 [CX4013]  
C8051F327-GM@QFN28 [CX4013] C8051F327-GQ@QFN28 [CX4013]  
C8051F330@MLP20 [CX4011] C8051F330D [CX0001]  
C8051F330-GM@MLP20 [CX4011] C8051F330-GM@MLP20(ISP) [CX0001]  
C8051F330-GP [CX0001] C8051F331@MLP20 [CX4011]  
C8051F331-GM@MLP20 [CX4011] C8051F332@MLP20 [CX4011]  
C8051F332-GM@MLP20 [CX4011] C8051F333@MLP20 [CX4011]  
C8051F333-GM@MLP20 [CX4011] C8051F334@MLP20 [CX4011]  
C8051F334-GM@MLP20 [CX4011] C8051F335@MLP20 [CX4011]  
C8051F335-GM@MLP20 [CX4011] C8051F336@MLP20 [CX4011]  
C8051F336-GM@MLP20 [CX4011] C8051F337@MLP20 [CX4011]  
C8051F337-GM@MLP20 [CX4011] C8051F338@MLP24 [CX4012]  
C8051F338-GM@MLP24 [CX4012] C8051F339@MLP24 [CX4012]  
C8051F339-GM@MLP24 [CX4012] C8051F340@TQFP48 [CX3007]  
C8051F340-GQ@TQFP48 [CX3007] C8051F341@TQFP48 [CX3007]  
C8051F341-GQ@TQFP48 [CX3007] C8051F342@LQFP32 [CX3001]  
C8051F342-GQ@LQFP32 [CX3001] C8051F343@LQFP32 [CX3001]  
C8051F343-GQ@LQFP32 [CX3001] C8051F344@TQFP48 [CX3007]  
C8051F344-GQ@TQFP48 [CX3007] C8051F345@TQFP48 [CX3007]  
C8051F345-GQ@TQFP48 [CX3007] C8051F346@LQFP32 [CX3001]  
C8051F346-GQ@LQFP32 [CX3001] C8051F347@LQFP32 [CX3001]  
C8051F347-GQ@LQFP32 [CX3001] C8051F348@TQFP48 [CX3007]  
C8051F348-GQ@TQFP48 [CX3007] C8051F349@LQFP32 [CX3001]  
C8051F349-GQ@LQFP32 [CX3001] C8051F34A@LQFP32 [CX3001]

C8051F34A-GQ@LQFP32 [CX3001]  
C8051F34B-GQ@LQFP32 [CX3001]  
C8051F34D@LQFP32 [CX3001]  
C8051F351-GM@QFN28 [CX4013]  
C8051F353-GM@QFN28 [CX4013]  
C8051F361@QFP32 [CX3001]  
C8051F363@QFP48 [CX3007]  
C8051F365@QFN28 [CX4013]  
C8051F367@QFN28 [CX4013]  
C8051F369@QFN28 [CX4013]  
C8051F370-GM [CX4012]  
C8051F371-GM [CX4012]  
C8051F374-GM [CX4012]  
C8051F375-GM [CX4012]  
C8051F381@QFN32 [CX4015]  
C8051F382@TQFP48 [CX3007]  
C8051F383@TQFP32 [CX3001]  
C8051F385@QFN32 [CX4015]  
C8051F386@TQFP48 [CX3007]  
C8051F387@TQFP32 [CX3001]  
C8051F390-GM [CX4012]  
C8051F391-GM [CX4012]  
C8051F392-GM [CX4011]  
C8051F393-GM [CX4011]  
C8051F394-GM [CX4012]  
C8051F395-GM [CX4012]  
C8051F396-GM [CX4011]  
C8051F397-GM [CX4011]  
C8051F398-GM [CX4011]  
C8051F399-GM [CX4011]  
C8051F410-GQ@LQFP32 [CX3001]  
C8051F411-GM@QFN28 [CX4013]  
C8051F412-GQ@LQFP32 [CX3001]  
C8051F413-GM@QFN28 [CX4013]  
C8051F500-IQ@QFP48 [CX3007]  
C8051F501-IQ@QFP48 [CX3007]  
C8051F502-IQ@QFP32 [CX3001]  
C8051F503-IQ@QFP32 [CX3001]  
C8051F504-IQ@QFP48 [CX3007]  
C8051F505-IQ@QFP48 [CX3007]  
C8051F506-IQ@QFP32 [CX3001]  
C8051F507-IQ@QFP32 [CX3001]  
C8051F509-IM@QFN40 [CX4017]  
C8051F511-IM@QFN40 [CX4017]  
C8051F520-IM@QFN10 [CX4007]  
C8051F521-IM@QFN10 [CX4007]  
C8051F523-IM@QFN10 [CX4007]  
C8051F524-IM@QFN10 [CX4007]  
C8051F526-IM@QFN10 [CX4007]  
C8051F527-IM@QFN10 [CX4007]  
C8051F530A-IT@TSSOP20 [CX1000]  
C8051F530-IT@TSSOP20 [CX1000]  
C8051F531A-IT@TSSOP20 [CX1000]  
C8051F531-IT@TSSOP20 [CX1000]  
C8051F533A-IT@TSSOP20 [CX1000]  
C8051F533-IT@TSSOP20 [CX1000]  
C8051F534A-IT@TSSOP20 [CX1000]  
C8051F534-IT@TSSOP20 [CX1000]  
C8051F536A-IT@TSSOP20 [CX1000]

C8051F34B@LQFP32 [CX3001]  
C8051F34C@TQFP48 [CX3007]  
C8051F350-GQ@LQFP32 [CX3001]  
C8051F352-GQ@LQFP32 [CX3001]  
C8051F360@QFP48 [CX3007]  
C8051F362@QFN28 [CX4013]  
C8051F364@QFP32 [CX3001]  
C8051F366@QFP32 [CX3001]  
C8051F368@QFP32 [CX3001]  
C8051F370-A-GM [CX4012]  
C8051F371-A-GM [CX4012]  
C8051F374-A-GM [CX4012]  
C8051F375-A-GM [CX4012]  
C8051F380@TQFP48 [CX3007]  
C8051F381@TQFP32 [CX3001]  
C8051F383@QFN32 [CX4015]  
C8051F384@TQFP48 [CX3007]  
C8051F385@TQFP32 [CX3001]  
C8051F387@QFN32 [CX4015]  
C8051F390-A-GM [CX4012]  
C8051F391-A-GM [CX4012]  
C8051F392-A-GM [CX4011]  
C8051F393-A-GM [CX4011]  
C8051F394-A-GM [CX4012]  
C8051F395-A-GM [CX4012]  
C8051F396-A-GM [CX4011]  
C8051F397-A-GM [CX4011]  
C8051F398-A-GM [CX4011]  
C8051F399-A-GM [CX4011]  
C8051F410@LQFP32 [CX3001]  
C8051F411@QFN28 [CX4013]  
C8051F412@LQFP32 [CX3001]  
C8051F413@QFN28 [CX4013]  
C8051F500-IM@QFN48 [CX4021]  
C8051F501-IM@QFN48 [CX4021]  
C8051F502-IM@QFN32 [CX4015]  
C8051F503-IM@QFN32 [CX4015]  
C8051F504-IM@QFN48 [CX4021]  
C8051F505-IM@QFN48 [CX4021]  
C8051F506-IM@QFN32 [CX4015]  
C8051F507-IM@QFN32 [CX4015]  
C8051F508-IM@QFN40 [CX4017]  
C8051F510-IM@QFN40 [CX4017]  
C8051F520A-IM@QFN10 [CX4007]  
C8051F521A-IM@QFN10 [CX4007]  
C8051F523A-IM@QFN10 [CX4007]  
C8051F524A-IM@QFN10 [CX4007]  
C8051F526A-IM@QFN10 [CX4007]  
C8051F527A-IM@QFN10 [CX4007]  
C8051F530A-IM@QFN20 [CX4011]  
C8051F530-IM@QFN20 [CX4011]  
C8051F531A-IM@QFN20 [CX4011]  
C8051F531-IM@QFN20 [CX4011]  
C8051F533A-IM@QFN20 [CX4011]  
C8051F533-IM@QFN20 [CX4011]  
C8051F534A-IM@QFN20 [CX4011]  
C8051F534-IM@QFN20 [CX4011]  
C8051F536A-IM@QFN20 [CX4011]  
C8051F536-IM@QFN20 [CX4011]

C8051F536-IT@TSSOP20 [CX1000]      C8051F537A-IM@QFN20 [CX4011]  
C8051F537A-IT@TSSOP20 [CX1000]      C8051F537-IM@QFN20 [CX4011]  
C8051F537-IT@TSSOP20 [CX1000]      C8051F540-IM@QFN32 [CX4015]  
C8051F540-IQ@QFP32 [CX3001]      C8051F541-IM@QFN32 [CX4015]  
C8051F541-IQ@QFP32 [CX3001]      C8051F542-IM@QFN24 [CX4012]  
C8051F543-IM@QFN24 [CX4012]      C8051F544-IM@QFN32 [CX4015]  
C8051F544-IQ@QFP32 [CX3001]      C8051F545-IM@QFN32 [CX4015]  
C8051F545-IQ@QFP32 [CX3001]      C8051F546-IM@QFN24 [CX4012]  
C8051F547-IM@QFN24 [CX4012]      C8051F550-IM@QFN24 [CX4012]  
C8051F551-IM@QFN24 [CX4012]      C8051F552-IM@QFN24 [CX4012]  
C8051F553-IM@QFN24 [CX4012]      C8051F554-IM@QFN24 [CX4012]  
C8051F555-IM@QFN24 [CX4012]      C8051F556-IM@QFN24 [CX4012]  
C8051F557-IM@QFN24 [CX4012]      C8051F560-IM@QFN32 [CX4015]  
C8051F560-IQ@QFP32 [CX3001]      C8051F561-IM@QFN32 [CX4015]  
C8051F561-IQ@QFP32 [CX3001]      C8051F562-IM@QFN32 [CX4015]  
C8051F562-IQ@QFP32 [CX3001]      C8051F563-IM@QFN32 [CX4015]  
C8051F563-IQ@QFP32 [CX3001]      C8051F564-IM@QFN32 [CX4015]  
C8051F564-IQ@QFP32 [CX3001]      C8051F565-IM@QFN32 [CX4015]  
C8051F565-IQ@QFP32 [CX3001]      C8051F566-IM@QFN32 [CX4015]  
C8051F566-IQ@QFP32 [CX3001]      C8051F567-IM@QFN32 [CX4015]  
C8051F567-IQ@QFP32 [CX3001]      C8051F568-IM@QFN40 [CX4017]  
C8051F569-IM@QFN40 [CX4017]      C8051F570-IM@QFN40 [CX4017]  
C8051F571-IM@QFN40 [CX4017]      C8051F572-IM@QFN40 [CX4017]  
C8051F573-IM@QFN40 [CX4017]      C8051F574-IM@QFN40 [CX4017]  
C8051F575-IM@QFN40 [CX4017]      C8051F580-AM@QFN48 [CX4021]  
C8051F580-AQ@QFP48 [CX3047]      C8051F580-IM@QFN48 [CX4021]  
C8051F580-IQ@QFP48 [CX3047]      C8051F581-AM@QFN48 [CX4021]  
C8051F581-AQ@QFP48 [CX3047]      C8051F581-IM@QFN48 [CX4021]  
C8051F581-IQ@QFP48 [CX3047]      C8051F582-AM@QFN32 [CX4015]  
C8051F582-AQ@QFP32 [CX3001]      C8051F582-IM@QFN32 [CX4015]  
C8051F582-IQ@QFP32 [CX3001]      C8051F583-AM@QFN32 [CX4015]  
C8051F583-AQ@QFP32 [CX3001]      C8051F583-IM@QFN32 [CX4015]  
C8051F583-IQ@QFP32 [CX3001]      C8051F584-AM@QFN48 [CX4021]  
C8051F584-AQ@QFP48 [CX3047]      C8051F584-IM@QFN48 [CX4021]  
C8051F584-IQ@QFP48 [CX3047]      C8051F585-AM@QFN48 [CX4021]  
C8051F585-AQ@QFP48 [CX3047]      C8051F585-IM@QFN48 [CX4021]  
C8051F585-IQ@QFP48 [CX3047]      C8051F586-AM@QFN32 [CX4015]  
C8051F586-AQ@QFP32 [CX3001]      C8051F586-IM@QFN32 [CX4015]  
C8051F586-IQ@QFP32 [CX3001]      C8051F587-AM@QFN32 [CX4015]  
C8051F587-AQ@QFP32 [CX3001]      C8051F587-IM@QFN32 [CX4015]  
C8051F587-IQ@QFP32 [CX3001]      C8051F588-AM@QFN40 [CX4017]  
C8051F588-IM@QFN40 [CX4017]      C8051F589-AM@QFN40 [CX4017]  
C8051F589-IM@QFN40 [CX4017]      C8051F590-AM@QFN40 [CX4017]  
C8051F590-IM@QFN40 [CX4017]      C8051F591-AM@QFN40 [CX4017]  
C8051F591-IM@QFN40 [CX4017]      C8051F700-GQ@QFP64 [CX3011]  
C8051F701-GQ@QFP64 [CX3011]      C8051F702-GQ@QFP64 [CX3011]  
C8051F703-GQ@QFP64 [CX3011]      C8051F704-GM@QFN48 [CX4021]  
C8051F704-GQ@QFP48 [CX3047]      C8051F705-GM@QFN48 [CX4021]  
C8051F705-GQ@QFP48 [CX3047]      C8051F706-GM@QFN48 [CX4021]  
C8051F706-GQ@QFP48 [CX3047]      C8051F707-GM@QFN48 [CX4021]  
C8051F707-GQ@QFP48 [CX3047]      C8051F708-GQ@QFP64 [CX3011]  
C8051F709-GQ@QFP64 [CX3011]      C8051F710-GQ@QFP64 [CX3011]  
C8051F711-GQ@QFP64 [CX3011]      C8051F712-GM@QFN48 [CX4021]  
C8051F712-GQ@QFP48 [CX3047]      C8051F713-GM@QFN48 [CX4021]  
C8051F713-GQ@QFP48 [CX3047]      C8051F714-GM@QFN48 [CX4021]  
C8051F714-GQ@QFP48 [CX3047]      C8051F715-GM@QFN48 [CX4021]  
C8051F715-GQ@QFP48 [CX3047]      C8051F716-GM [CX4015]  
C8051F717-GM [CX4012]      C8051F750B-GM [CX4021]  
C8051F750B-GM1 [CX4043]      C8051F750-GM [CX4021]

C8051F750-GM1 [CX4043]  
C8051F751-GM [CX4015]  
C8051F752-GM [CX4012]  
C8051F755B-GM1 [CX4043]  
C8051F755-GM1 [CX4043]  
C8051F756-GM [CX4015]  
C8051F757-GM [CX4012]  
C8051F760-GM1 [CX4043]  
C8051F762-GM [CX4012]  
C8051F765-GM1 [CX4043]  
C8051F767-GM [CX4012]  
C8051F800-GU@QSOP24 [CX1001]  
C8051F801-GU@QSOP24 [CX1001]  
C8051F802-GU@QSOP24 [CX1001]  
C8051F804-GS@SOIC16 [CX1016]  
C8051F806-GM@QFN20 [CX4011]  
C8051F807-GM@QFN20 [CX4011]  
C8051F808-GM@QFN20 [CX4011]  
C8051F809-GS@SOIC16 [CX1016]  
C8051F811-GS@SOIC16 [CX1016]  
C8051F812-GU@QSOP24 [CX1001]  
C8051F813-GU@QSOP24 [CX1001]  
C8051F814-GU@QSOP24 [CX1001]  
C8051F816-GS@SOIC16 [CX1016]  
C8051F818-GM@QFN20 [CX4011]  
C8051F819-GM@QFN20 [CX4011]  
C8051F820-GM@QFN20 [CX4011]  
C8051F821-GS@SOIC16 [CX1016]  
C8051F823-GS@SOIC16 [CX1016]  
C8051F825-GS@SOIC16 [CX1016]  
C8051F827-GS@SOIC16 [CX1016]  
C8051F829-GS@SOIC16 [CX1016]  
C8051F831-GS@SOIC16 [CX1016]  
C8051F833-GS@SOIC16 [CX1016]  
C8051F835-GS@SOIC16 [CX1016]  
C8051F901-GU@QSOP24 [CX1001]  
C8051F902-GU@QSOP24 [CX1001]  
C8051F911-GU@QSOP24 [CX1001]  
C8051F912-GU@QSOP24 [CX1001]  
C8051F920-F-GQ@LQFP32 [CX3001]  
C8051F920-GQ@LQFP32 [CX3001]  
C8051F921-GM@QFN24 [CX4012]  
C8051F930-F-GQ@LQFP32 [CX3001]  
C8051F930-GQ@LQFP32 [CX3001]  
C8051F931-GM@QFN24 [CX4012]  
C8051F960A-GQ [CX3016]  
C8051F960-GQ [CX3016]  
C8051F961-GM [CX4017]  
C8051F962A-GQ [CX3016]  
C8051F962-GQ [CX3016]  
C8051F963-GM [CX4017]  
C8051F964A-GQ [CX3016]  
C8051F964-GQ [CX3016]  
C8051F965-GM [CX4017]  
C8051F966A-GQ [CX3016]  
C8051F966-GQ [CX3016]  
C8051F967-GM [CX4017]  
C8051F968A-GQ [CX3016]  
C8051F968-GQ [CX3016]  
C8051F751B-GM [CX4015]  
C8051F752B-GM [CX4012]  
C8051F755B-GM [CX4021]  
C8051F755-GM [CX4021]  
C8051F756B-GM [CX4015]  
C8051F757B-GM [CX4012]  
C8051F760-GM [CX4021]  
C8051F761-GM [CX4015]  
C8051F765-GM [CX4021]  
C8051F766-GM [CX4015]  
C8051F800-GM@QFN20 [CX4011]  
C8051F801-GM@QFN20 [CX4011]  
C8051F802-GM@QFN20 [CX4011]  
C8051F803-GS@SOIC16 [CX1016]  
C8051F805-GS@SOIC16 [CX1016]  
C8051F806-GU@QSOP24 [CX1001]  
C8051F807-GU@QSOP24 [CX1001]  
C8051F808-GU@QSOP24 [CX1001]  
C8051F810-GS@SOIC16 [CX1016]  
C8051F812-GM@QFN20 [CX4011]  
C8051F813-GM@QFN20 [CX4011]  
C8051F814-GM@QFN20 [CX4011]  
C8051F815-GS@SOIC16 [CX1016]  
C8051F817-GS@SOIC16 [CX1016]  
C8051F818-GU@QSOP24 [CX1001]  
C8051F819-GU@QSOP24 [CX1001]  
C8051F820-GU@QSOP24 [CX1001]  
C8051F822-GS@SOIC16 [CX1016]  
C8051F824-GS@SOIC16 [CX1016]  
C8051F826-GS@SOIC16 [CX1016]  
C8051F828-GS@SOIC16 [CX1016]  
C8051F830-GS@SOIC16 [CX1016]  
C8051F832-GS@SOIC16 [CX1016]  
C8051F834-GS@SOIC16 [CX1016]  
C8051F901-GM@QFN24 [CX4012]  
C8051F902-GM@QFN24 [CX4012]  
C8051F911-GM@QFN24 [CX4012]  
C8051F912-GM@QFN24 [CX4012]  
C8051F920-F-GM@QFN32 [CX4015]  
C8051F920-GM@QFN32 [CX4015]  
C8051F921-F-GM@QFN24 [CX4012]  
C8051F930-F-GM@QFN32 [CX4015]  
C8051F930-GM@QFN32 [CX4015]  
C8051F931-F-GM@QFN24 [CX4012]  
C8051F960A-GM [CX0001]  
C8051F960-GM [CX0001]  
C8051F961A-GM [CX4017]  
C8051F962A-GM [CX0001]  
C8051F962-GM [CX0001]  
C8051F963A-GM [CX4017]  
C8051F964A-GM [CX0001]  
C8051F964-GM [CX0001]  
C8051F965A-GM [CX4017]  
C8051F966A-GM [CX0001]  
C8051F966-GM [CX0001]  
C8051F967A-GM [CX4017]  
C8051F968A-GM [CX0001]  
C8051F968-GM [CX0001]  
C8051F969A-GM [CX4017]

C8051F969-GM [CX4017]	C8051F980-GM [CX4038]
C8051F981-GM [CX4038]	C8051F982-GM [CX4038]
C8051F983-GM [CX4038]	C8051F985-GM [CX4038]
C8051F986-GM [CX4012]	C8051F986-GU [CX1001]
C8051F987-GM [CX4012]	C8051F987-GU [CX1001]
C8051F988-GM [CX4012]	C8051F988-GU [CX1001]
C8051F989-GM [CX4012]	C8051F989-GU [CX1001]
C8051F990-GM [CX4038]	C8051F991-GM [CX4038]
C8051F996-GM [CX4012]	C8051F996-GU [CX1001]
C8051F997-GM [CX4012]	C8051F997-GU [CX1001]
C8051T320-GQ@LQFP32 [CX3001]	C8051T321-GM@QFN28 [CX4013]
C8051T322-GQ@LQFP32 [CX3001]	C8051T323-GM@QFN28 [CX4013]
C8051T326-GM@QFN28 [CX4013]	C8051T327-GM@QFN28 [CX4013]
C8051T600@QFN11 [CX4007]	C8051T600@TSSOP14 [CX1016]
C8051T601@QFN11 [CX4007]	C8051T601@TSSOP14 [CX1016]
C8051T602@QFN11 [CX4007]	C8051T602@TSSOP14 [CX1016]
C8051T603@QFN11 [CX4007]	C8051T603@TSSOP14 [CX1016]
C8051T604@QFN11 [CX4007]	C8051T604@TSSOP14 [CX1016]
C8051T605@QFN11 [CX4007]	C8051T605@TSSOP14 [CX1016]
C8051T606@MSOP10 [CX1051]	C8051T606@QFN10 [CX4035]
C8051T606@QFN11 [CX4007]	C8051T610-GQ@LQFP32 [CX3001]
C8051T610-GQ@LQFP32(old) [CX3001]	C8051T611-GM@QFN28(old) [CX4013]
C8051T611-GM@QFN28 [CX4013]	
C8051T612-GQ@LQFP32 [CX3001]	
C8051T612-GQ@LQFP32(old) [CX3001]	
C8051T613-GM@QFN28 [CX4013]	C8051T613-GM@QFN28(old) [CX4013]
C8051T614-GQ@LQFP32 [CX3001]	
C8051T614-GQ@LQFP32(old) [CX3001]	
C8051T615-GM@QFN28 [CX4013]	C8051T615-GM@QFN28(old) [CX4013]
C8051T616-GM@QFN24 [CX4012]	C8051T616-GM@QFN24(old) [CX4012]
C8051T617-GM@QFN24 [CX4012]	C8051T617-GM@QFN24(old) [CX4012]
C8051T620-GM@QFN32 [CX4015]	C8051T621-GM@QFN32 [CX4015]
C8051T622-GM@QFN24 [CX4012]	C8051T623-GM@QFN24 [CX4012]
C8051T626-B-GM [CX4015]	C8051T627-B-GM [CX4015]
SI1020_A_GM(ISP) [CX0001]	SI1021_A_GM(ISP) [CX0001]
SI1022_A_GM(ISP) [CX0001]	SI1023_A_GM(ISP) [CX0001]
SI1024_A_GM(ISP) [CX0001]	SI1025_A_GM(ISP) [CX0001]
SI1026_A_GM(ISP) [CX0001]	SI1027_A_GM(ISP) [CX0001]
SI1030_A_GM(ISP) [CX0001]	SI1031_A_GM(ISP) [CX0001]
SI1032_A_GM(ISP) [CX0001]	SI1033_A_GM(ISP) [CX0001]
SI1034_A_GM(ISP) [CX0001]	SI1035_A_GM(ISP) [CX0001]
SI1036_A_GM(ISP) [CX0001]	SI1037_A_GM(ISP) [CX0001]
SI8250@LQFP32 [CX3001]	SI8250@QFN28 [CX4013]
SI8250-IM@QFN28 [CX4013]	SI8250-IQ@LQFP32 [CX3001]
SI8251@LQFP32 [CX3001]	SI8251@QFN28 [CX4013]
SI8251-IM@QFN28 [CX4013]	SI8251-IQ@LQFP32 [CX3001]
SI8252@LQFP32 [CX3001]	SI8252@QFN28 [CX4013]
SI8252-IM@QFN28 [CX4013]	SI8252-IQ@LQFP32 [CX3001]

## SILICON7

### E (E) PROM/FRAM/NVRAM

SV4E1602UBA@FBGA56 [CX5045]	SV4E1602UTA@FBGA56 [CX5045]
SV4E1604UBA@FBGA56 [CX5045]	SV4E1604UTA@FBGA56 [CX5045]
SV4E1608UBA@FBGA56 [CX5045]	SV4E1608UTA@FBGA56 [CX5045]
SV4E3204UBA@FBGA56 [CX5045]	SV4E3204UTA@FBGA56 [CX5045]
SV4E3208UBA@FBGA56 [CX5001]	SV4E3208UTA@FBGA56 [CX5045]

SV4E3216UBA@FBGA56 [CX5045]	SV4E3216UTA@FBGA56 [CX5045]
SV4F1602UBA@FBGA66 [CX5005]	SV4F1602UTA@FBGA66 [CX5005]
SV4F1604UBA@FBGA66 [CX5005]	SV4F1604UTA@FBGA66 [CX5005]
SV4F1608UBA@FBGA66 [CX5005]	SV4F1608UTA@FBGA66 [CX5005]
SV4F3204UBA@FBGA66 [CX5005]	SV4F3204UTA@FBGA66 [CX5005]
SV4F3208UBA@FBGA66 [CX5005]	SV4F3208UTA@FBGA66 [CX5005]
SV4F3216UBA@FBGA66 [CX5005]	SV4F3216UTA@FBGA66 [CX5005]
SV5C2832UCR@FBGA72 [CX5001]	
SV5C3238UBA(NO EFP)@FBGA72 [CX5001]	
SV5C3238UBA@FBGA72 [CX5001]	
SV5C3238UTA(NO EFP)@FBGA72 [CX5001]	
SV5C3238UTA@FBGA72 [CX5001]	
SV5C6408UBR(NO EFP)@FBGA72 [CX5001]	
SV5C6408UBR@FBGA72 [CX5001]	
SV5C6408UTR(NO EFP)@FBGA72 [CX5001]	
SV5C6408UTR@FBGA72 [CX5001]	
SV5C6416UBB(NO EFP)@FBGA72 [CX5001]	
SV5C6416UBB@FBGA72 [CX5001]	
SV5C6416UBR(NO EFP)@FBGA72 [CX5001]	
SV5C6416UBR@FBGA72 [CX5001]	
SV5C6416UTB(NO EFP)@FBGA72 [CX5001]	
SV5C6416UTB@FBGA72 [CX5001]	
SV5C6416UTR(NO EFP)@FBGA72 [CX5001]	
SV5C6416UTR@FBGA72 [CX5001]	
SV5C6432UBR(NO EFP)@FBGA72 [CX5001]	
SV5C6432UBR@FBGA72 [CX5001]	
SV5C6432UTR(NO EFP)@FBGA72 [CX5001]	
SV5C6432UTR@FBGA72 [CX5001]	SV5D2832UCA@FBGA88 [CX5005]
SV6C2832UBA@FBGA72 [CX5001]	SV6C2832UTA@FBGA72 [CX5001]
SV6C2864UBA@FBGA72 [CX5001]	SV6C2864UTA@FBGA72 [CX5001]
SV6C6416UBA@FBGA72 [CX5001]	SV6C6416UTA@FBGA72 [CX5001]
SV6C6432UBA@FBGA72 [CX5001]	SV6C6432UTA@FBGA72 [CX5001]
SV6D2832UBA@FBGA88 [CX5001]	SV6D2832UTA@FBGA88 [CX5001]
SV7C1602UBA@FBGA72 [CX5001]	SV7C1602UTA@FBGA72 [CX5001]
SV7C1604UBA@FBGA72 [CX5001]	SV7C1604UTA@FBGA72 [CX5001]
SV7C1608UBA@FBGA72 [CX5001]	SV7C1608UTA@FBGA72 [CX5001]
SV7C3204UBA@FBGA72 [CX5001]	SV7C3204UTA@FBGA72 [CX5001]
SV7C3208UBA@FBGA72 [CX5001]	SV7C3208UTA@FBGA72 [CX5001]
SV7C3216UBA@FBGA72 [CX5001]	SV7C3216UTA@FBGA72 [CX5001]
SV7E1602UBA@FBGA56 [CX5001]	SV7E1602UBAL@FBGA56 [CX5045]
SV7E1602UTA@FBGA56 [CX5001]	SV7E1602UTAL@FBGA56 [CX5045]
SV7E1604UBA@FBGA56 [CX5001]	SV7E1604UBAL@FBGA56 [CX5045]
SV7E1604UTA@FBGA56 [CX5001]	SV7E1604UTAL@FBGA56 [CX5045]
SV7E1608UBA@FBGA56 [CX5001]	SV7E1608UBALC@FBGA56 [CX5045]
SV7E1608UTA@FBGA56 [CX5001]	SV7E1608UTALC@FBGA56 [CX5045]
SV7E3204UBA@FBGA56 [CX5001]	SV7E3204UBAL@FBGA56 [CX5045]
SV7E3204UTA@FBGA56 [CX5001]	SV7E3204UTAL@FBGA56 [CX5045]
SV7E3208UBA@FBGA56 [CX5001]	SV7E3208UBALC@FBGA56 [CX5045]
SV7E3208UTA@FBGA56 [CX5001]	SV7E3208UTALC@FBGA56 [CX5045]
SV7E3216UBA@FBGA56 [CX5001]	SV7E3216UBALC@FBGA56 [CX5045]
SV7E3216UTA@FBGA56 [CX5001]	SV7E3216UTALC@FBGA56 [CX5045]
SVME2832UBA@FBGA56 [CX5045]	SVME2832UTA@FBGA56 [CX5045]
SVME2864UBA@FBGA56 [CX5045]	SVME2864UTA@FBGA56 [CX5045]
SVME3204UBA@FBGA56 [CX5045]	SVME3204UTA@FBGA56 [CX5045]
SVME3208UBA@FBGA56 [CX5045]	SVME3208UTA@FBGA56 [CX5045]
SVME3216UBA@FBGA56 [CX5045]	SVME3216UTA@FBGA56 [CX5045]
SVME6416UBA@FBGA56 [CX5045]	SVME6416UTA@FBGA56 [CX5045]
SVME6432UBA@FBGA56 [CX5045]	SVME6432UTA@FBGA56 [CX5045]

## SIMTEK

### E (E) PROM/FRAM/NVRAM

STK10C48 [CX0001]  
STK10C48@SOIC28(300 mil) [CX1033]  
STK10C48@SOIC28(350 mil) [CX1035]  
STK10C68 [CX0001] STK10C68@PLCC28 [CX2028]  
STK10C68@SOIC28 [CX1035] STK11C48 [CX0001]  
STK11C48@SOIC28(300 mil) [CX1033]  
STK11C48@SOIC28(350 mil) [CX1035]  
STK11C68 [CX0001] STK11C68@PLCC28 [CX2028]  
STK11C68@SOIC28 [CX1035] STK11C88 [CX0001]  
STK11C88(3V) [CX0001]  
STK11C88(3V)@SOIC28(300 mil) [CX1033]  
STK11C88(3V)@SOIC28(350 mil) [CX1035]  
STK11C88@SOIC28(300 mil) [CX1033]  
STK11C88@SOIC28(350 mil) [CX1035]  
STK12C68 [CX0001] STK12C68@PLCC28 [CX2028]  
STK12C68@SOIC28 [CX1035] STK14C88 [CX0001]  
STK14C88(3V) [CX0001] STK14C88(3V)@PLCC32 [CX2032]  
STK14C88(3V)@SOIC32(300 mil) [CX1036]  
STK14C88(3V)@SOIC32(350 mil) [CX1035]  
STK14C88@PLCC32 [CX2032]  
STK14C88@SOIC32(300 mil) [CX1036]  
STK14C88@SOIC32(350 mil) [CX1035]  
STK15C68 [CX0001] STK15C68@SOIC28 [CX1035]  
STK15C88 [CX0001]  
STK15C88@SOIC28(300 mil) [CX1033]  
STK15C88@SOIC28(350 mil) [CX1035]  
STK16C68 [CX0001] STK16C88 [CX0001]  
STK16C88(3V) [CX0001] STK20C04 [CX0001]  
STK22C48 [CX0001]  
STK22C48@SOIC28(300 mil) [CX1033]  
STK22C48@SOIC28(350 mil) [CX1035]  
STK25C48 [CX0001]

## SINOWEALTH

### MICROCONTROLLER

SH66P51A@LQFP44 [CX3002] SH66P51A@LQFP64 [CX3057]  
SH67P33 [CX0001] SH67P33@SOIC20 [CX1033]  
SH67P33@SSOP20 [CX1067] SH67P33C [CX0001]  
SH67P33C@SOIC20 [CX1033] SH67P33C@SSOP20 [CX1067]  
SH79F081AM [CX1036] SH79F161A [CX3001]  
SH79F161A@QFP32 [CX3001] SH79F161A@QFP44 [CX3002]  
SH79F166@QFP44 [CX3002] SH79F166A@QFP44 [CX3002]  
SH79F166F@QFP44 [CX3002]

## SIRF

### E (E) PROM/FRAM/NVRAM

GSC3F-7990@FBGA140 [CX5065]



# SMI

## MICROCONTROLLER

SM3712@QFN40 [CX4039]

SM3732@QFN40 [CX4039-2]

# SMOS

## E (E) PROM/FRAM/NVRAM

SPM27128 [CX0001]  
SPM27C256 [CX0001]  
SPM27C64H [CX0001]

SPM27128C [CX0001]  
SPM27C64 [CX0001]

# SONIX

## MICROCONTROLLER

SN8P1504 [CX0001]  
SN8P1504@SOP28 [CX1033]  
SN8P1507@TQFP44 [CX3002]  
SN8P1602@SOP18 [CX1033]  
SN8P1603 [CX0001]  
SN8P1603@SSOP20 [CX1025]  
SN8P1604@SOP28 [CX1033]  
SN8P1702@SOP18 [CX1033]  
SN8P1704A [CX0001]  
SN8P1704B [CX0001]  
SN8P1706A [CX0001]  
SN8P1707A [CX0001]  
SN8P1707B@TQFP44 [CX3002]  
SN8P1708A@SSOP48 [CX1028]  
SN8P1708B@SSOP48 [CX1028]  
SN8P1714@SOP18 [CX1033]  
SN8P1716 [CX0001]  
SN8P2501AP [CX0001]  
SN8P2501AX@TSSOP16 [CX1000]  
SN8P2501BS@SOP14 [CX1016]  
SN8P2502AP [CX0001]  
SN8P2502AX@TSSOP16 [CX1000]  
SN8P2502BS@SOP14 [CX1016]  
SN8P2504AP [CX0001]  
SN8P2504AX@TSSOP16 [CX1000]  
SN8P2504BS@SOP14 [CX1016]  
SN8P2602AP [CX0001]  
SN8P2602AX@SSOP20 [CX1025]  
SN8P2602BS@SOP18 [CX1031]  
SN8P2603AP [CX0001]  
SN8P2603AX@SSOP20 [CX1025]  
SN8P2603BS@SOP18 [CX1031]  
SN8P26042AP [CX0001]  
SN8P26042AX@SSOP20 [CX1025]  
SN8P26042BS@SOP20 [CX1031]  
SN8P26042P [CX0001]  
SN8P26042X@SSOP20 [CX1025]  
SN8P2604AS@SOP28 [CX1033]  
SN8P2604BK [CX0001]

SN8P1504@SOP18 [CX1033]  
SN8P1506 [CX0001]  
SN8P1602 [CX0001]  
SN8P1602@SSOP20 [CX1025]  
SN8P1603@SOP18 [CX1033]  
SN8P1604 [CX0001]  
SN8P1702 [CX0001]  
SN8P1702@SSOP20 [CX1025]  
SN8P1704A@SOP28 [CX1033]  
SN8P1704B@SOP28 [CX1033]  
SN8P1706B [CX0001]  
SN8P1707A@TQFP44 [CX3002]  
SN8P1708A [CX0001]  
SN8P1708B [CX0001]  
SN8P1714 [CX0001]  
SN8P1714@SOP28 [CX1033]  
SN8P1717@TQFP44 [CX3002]  
SN8P2501AS@SOP14 [CX1016]  
SN8P2501BP [CX0001]  
SN8P2501BX@TSSOP16 [CX1000]  
SN8P2502AS@SOP14 [CX1016]  
SN8P2502BP [CX0001]  
SN8P2502BX@TSSOP16 [CX1000]  
SN8P2504AS@SOP14 [CX1016]  
SN8P2504BP [CX0001]  
SN8P2504BX@TSSOP16 [CX1000]  
SN8P2602AS@SOP18 [CX1031]  
SN8P2602BP [CX0001]  
SN8P2602BX@SSOP20 [CX1025]  
SN8P2603AS@SOP18 [CX1031]  
SN8P2603BP [CX0001]  
SN8P2603BX@SSOP20 [CX1025]  
SN8P26042AS@SOP20 [CX1031]  
SN8P26042BP [CX0001]  
SN8P26042BX@SSOP20 [CX1025]  
SN8P26042S@SOP20 [CX1031]  
SN8P2604AK [CX0001]  
SN8P2604AX@SSOP28 [CX1026]  
SN8P2604BS@SOP28 [CX1033]

SN8P2604BX@SSOP28 [CX1026]  
SN8P2604S@SOP28 [CX1033]  
SN8P2606P [CX0001]  
SN8P2608X@SSOP48 [CX1028]  
SN8P2622S@SOP18 [CX1031]  
SN8P2624K [CX0001]  
SN8P2624X@SSOP28 [CX1026]  
SN8P2704AP [CX0001]  
SN8P2705AP [CX0001]  
SN8P2706AP [CX0001]  
SN8P2708AP [CX0001]  
SN8P2708AX@SSOP48 [CX1028]  
SN8P2722S@SOP20 [CX1031]

SN8P2604K [CX0001]  
SN8P2604X@SSOP28 [CX1026]  
SN8P2608P [CX0001]  
SN8P2622P [CX0001]  
SN8P2622X@SSOP20 [CX1024]  
SN8P2624S@SOP28 [CX1033]  
SN8P2704AK@SDIP28 [CX0032]  
SN8P2704AS@SOP28 [CX1018]  
SN8P2705AS@SOP32 [CX1020]  
SN8P2707AQ@QFP44 [CX3003]  
SN8P2708AQ@LQFP48 [CX3007]  
SN8P2722P [CX0001]  
SN8P2722X@SSOP20 [CX1024]

## SONY

### E (E) PROM/FRAM/NVRAM

CXK1011M@SOIC8 [CX1045]  
CXK1012P [CX0001]  
CXK1023P [CX0001]

CXK1011P [CX0001]  
CXK1013P [CX0001]  
CXK27C4001 [CX0001]

### DRAM & SRAM

CXK581000 [CX0001]

CXK581000@SOIC32 [CX1035]

## SPACE ELECTRONICS[SEi]

### E (E) PROM/FRAM/NVRAM

28C010 [CX0001]  
28C010@TSOP32 [CX1002]  
28C010T@PLCC32 [CX2032]  
28C011 [CX0001]  
28C011@TSOP32 [CX1002]  
28C011T@PLCC32 [CX2032]

28C010@PLCC32 [CX2032]  
28C010T [CX0001]  
28C010T@TSOP32 [CX1002]  
28C011@PLCC32 [CX2032]  
28C011T [CX0001]  
28C011T@TSOP32 [CX1002]

## SPANSION

### E (E) PROM/FRAM/NVRAM

AM29BDD160GB@FBGA80 [CX50UN]  
AM29BDD160GT@FBGA80 [CX50UN]  
AM29BL162CB@SSOP56 [CX1029]  
AM29DL161DB@FBGA48 [CX5022]  
AM29DL161DB@FBGA64 [CX5074]  
AM29DL161DB@VFBGA48 [CX5043]  
AM29DL161DT@FBGA63 [CX5047]  
AM29DL161DT@TSOP48 [CX1004]  
AM29DL162CB@FBGA48 [CX5022]  
AM29DL162CT@FBGA48 [CX5022]  
AM29DL162DB@FBGA48 [CX5022]  
AM29DL162DB@FBGA64 [CX5074]  
AM29DL162DB@VFBGA48 [CX5043]  
AM29DL162DT@FBGA63 [CX5047]

AM29BDD160GB@PQFP80 [CX3020]  
AM29BDD160GT@PQFP80 [CX3020]  
AM29BL802CB@SSOP56 [CX1029]  
AM29DL161DB@FBGA63 [CX5047]  
AM29DL161DB@TSOP48 [CX1004]  
AM29DL161DT@FBGA48 [CX5022]  
AM29DL161DT@FBGA64 [CX5074]  
AM29DL161DT@VFBGA48 [CX5043]  
AM29DL162CB@TSOP48 [CX1004]  
AM29DL162CT@TSOP48 [CX1004]  
AM29DL162DB@FBGA63 [CX5047]  
AM29DL162DB@TSOP48 [CX1004]  
AM29DL162DT@FBGA48 [CX5022]  
AM29DL162DT@FBGA64 [CX5074]

AM29DL162DT@TSOP48 [CX1004] AM29DL162DT@VFBGA48 [CX5043]  
AM29DL163CB@FBGA48 [CX5022] AM29DL163CB@TSOP48 [CX1004]  
AM29DL163CT@FBGA48 [CX5022] AM29DL163CT@TSOP48 [CX1004]  
AM29DL163DB@FBGA48 [CX5022] AM29DL163DB@FBGA63 [CX5047]  
AM29DL163DB@FBGA64 [CX5074] AM29DL163DB@TSOP48 [CX1004]  
AM29DL163DB@VFBGA48 [CX5043] AM29DL163DT@FBGA48 [CX5022]  
AM29DL163DT@FBGA63 [CX5047] AM29DL163DT@FBGA64 [CX5074]  
AM29DL163DT@TSOP48 [CX1004] AM29DL163DT@VFBGA48 [CX5043]  
AM29DL164CB@FBGA48 [CX5022] AM29DL164CB@TSOP48 [CX1004]  
AM29DL164CT@FBGA48 [CX5022] AM29DL164CT@TSOP48 [CX1004]  
AM29DL164DB@FBGA48 [CX5022] AM29DL164DB@FBGA63 [CX5047]  
AM29DL164DB@FBGA64 [CX5074] AM29DL164DB@TSOP48 [CX1004]  
AM29DL164DB@VFBGA48 [CX5043] AM29DL164DT@FBGA48 [CX5022]  
AM29DL164DT@FBGA63 [CX5047] AM29DL164DT@FBGA64 [CX5074]  
AM29DL164DT@TSOP48 [CX1004] AM29DL164DT@VFBGA48 [CX5043]  
AM29DL320GB@FBGA48 [CX5063] AM29DL320GB@FBGA63 [CX5051]  
AM29DL320GB@FBGA64 [CX5074] AM29DL320GB@TSOP48 [CX1004]  
AM29DL320GT@FBGA48 [CX5063] AM29DL320GT@FBGA63 [CX5051]  
AM29DL320GT@FBGA64 [CX5074] AM29DL320GT@TSOP48 [CX1004]  
AM29DL321CB@TSOP48 [CX1004] AM29DL321CT@TSOP48 [CX1004]  
AM29DL322CB@FBGA63 [CX5051] AM29DL322CB@TSOP48 [CX1004]  
AM29DL322CT@FBGA63 [CX5051] AM29DL322CT@TSOP48 [CX1004]  
AM29DL322DB@FBGA63 [CX5051] AM29DL322DB@TSOP48 [CX1004]  
AM29DL322DT@FBGA63 [CX5051] AM29DL322DT@TSOP48 [CX1004]  
AM29DL322GB@FBGA48 [CX5063] AM29DL322GB@FBGA63 [CX5051]  
AM29DL322GB@FBGA64 [CX5074] AM29DL322GB@TSOP48 [CX1004]  
AM29DL322GT@FBGA48 [CX5063] AM29DL322GT@FBGA63 [CX5051]  
AM29DL322GT@FBGA64 [CX5074] AM29DL322GT@TSOP48 [CX1004]  
AM29DL323CB@FBGA63 [CX5051] AM29DL323CB@TSOP48 [CX1004]  
AM29DL323CT@FBGA63 [CX5051] AM29DL323CT@TSOP48 [CX1004]  
AM29DL323DB@FBGA48 [CX5022] AM29DL323DB@FBGA63 [CX5051]  
AM29DL323DB@TSOP48 [CX1004] AM29DL323DT@FBGA48 [CX5022]  
AM29DL323DT@FBGA63 [CX5051] AM29DL323DT@TSOP48 [CX1004]  
AM29DL323GB@FBGA48 [CX5063] AM29DL323GB@FBGA63 [CX5051]  
AM29DL323GB@FBGA64 [CX5074] AM29DL323GB@TSOP48 [CX1004]  
AM29DL323GT@FBGA48 [CX5063] AM29DL323GT@FBGA63 [CX5051]  
AM29DL323GT@FBGA64 [CX5074] AM29DL323GT@TSOP48 [CX1004]  
AM29DL324CB@TSOP48 [CX1004] AM29DL324CT@TSOP48 [CX1004]  
AM29DL324DB@FBGA63 [CX5051] AM29DL324DB@TSOP48 [CX1004]  
AM29DL324DT@FBGA63 [CX5051] AM29DL324DT@TSOP48 [CX1004]  
AM29DL324GB@FBGA48 [CX5063] AM29DL324GB@FBGA63 [CX5051]  
AM29DL324GB@FBGA64 [CX5074] AM29DL324GB@TSOP48 [CX1004]  
AM29DL324GT@FBGA48 [CX5063] AM29DL324GT@FBGA63 [CX5051]  
AM29DL324GT@FBGA64 [CX5074] AM29DL324GT@TSOP48 [CX1004]  
AM29DL400BB (REVERSE)@TSOP48 [CX1004]  
AM29DL400BB@PSOP44 [CX1014] AM29DL400BB@TSOP48 [CX1004]  
AM29DL400BT (REVERSE)@TSOP48 [CX1004]  
AM29DL400BT@PLCC44 [CX1014] AM29DL400BT@TSOP48 [CX1004]  
AM29DL640D@FBGA63 [CX5041] AM29DL640D@TSOP48 [CX1004]  
AM29DL640G@FBGA63 [CX5041] AM29DL640G@FBGA64 [CX5074]  
AM29DL640G@TSOP48 [CX1004] AM29DL642G@FBGA63 [CX5041]  
AM29DL800B@PSOP44 [CX1014] AM29DL800B@TSOP48 [CX1004]  
AM29DL800BB (REVERSE)@TSOP48 [CX1004]  
AM29DL800BB@FBGA48 [CX5039] AM29DL800BB@PSOP44 [CX1014]  
AM29DL800BB@TSOP48 [CX1004]  
AM29DL800BT (REVERSE)@TSOP48 [CX1004]  
AM29DL800BT@FBGA48 [CX5039] AM29DL800BT@PSOP44 [CX1014]  
AM29DL800BT@TSOP48 [CX1004] AM29DL800T@PSOP44 [CX1014]  
AM29DL800T@TSOP48 [CX1004] AM29DS163CB@TSOP48 [CX1004]

AM29DS163CT@TSOP48 [CX1004] AM29DS163DB@FBGA48 [CX5002]  
AM29DS163DB@TSOP48 [CX1004] AM29DS163DT@FBGA48 [CX5002]  
AM29DS163DT@TSOP48 [CX1004] AM29DS323DB@FBGA48 [CX5002]  
AM29DS323DB@TSOP48 [CX1004] AM29DS323DT@FBGA48 [CX5002]  
AM29DS323DT@TSOP48 [CX1004] AM29F002B [CX0001]  
AM29F002B@PLCC32 [CX2032] AM29F002B@TSOP32 [CX1002]  
AM29F002BB [CX0001] AM29F002BB@PLCC32 [CX2032]  
AM29F002BB@TSOP32 [CX1002] AM29F002BT [CX0001]  
AM29F002BT@PLCC32 [CX2032] AM29F002BT@TSOP32 [CX1002]  
AM29F002NB [CX0001] AM29F002NB@PLCC32 [CX2032]  
AM29F002NB@TSOP32 [CX1002] AM29F002NBB [CX0001]  
AM29F002NBB@PLCC32 [CX2032] AM29F002NBB@TSOP32 [CX1002]  
AM29F002NBT [CX0001] AM29F002NBT@PLCC32 [CX2032]  
AM29F002NBT@TSOP32 [CX1002] AM29F002NT [CX0001]  
AM29F002NT@PLCC32 [CX2032] AM29F002NT@TSOP32 [CX1002]  
AM29F002T [CX0001] AM29F002T@PLCC32 [CX2032]  
AM29F002T@TSOP32 [CX1002] AM29F004BB [CX0001]  
AM29F004BB@PLCC32 [CX2032] AM29F004BB@TSOP32 [CX1002]  
AM29F004BT [CX0001] AM29F004BT@PLCC32 [CX2032]  
AM29F004BT@TSOP32 [CX1002] AM29F016@PSOP44 [CX1014]  
AM29F016@TSOP40 [CX1006] AM29F016@TSOP48 [CX1004]  
AM29F016B@PSOP44 [CX1014] AM29F016B@TSOP40 [CX1006]  
AM29F016B@TSOP48 [CX1004] AM29F016D@PSOP44 [CX1014]  
AM29F016D@TSOP40 [CX1006] AM29F016D@TSOP48 [CX1004]  
AM29F017B(REVERSE)@TSOP40 [CX1006] AM29F017B@TSOP48 [CX1004]  
AM29F017B(REVERSE)@TSOP48 [CX1004] AM29F017D@TSOP48 [CX1004]  
AM29F017D@TSOP40 [CX1006] AM29F032B@TSOP40 [CX1006]  
AM29F032B@PSOP44 [CX1014] AM29F040@PLCC32 [CX2032]  
AM29F040 [CX0001] AM29F040A [CX0001]  
AM29F040@TSOP32 [CX1002] AM29F040A@TSOP32 [CX1002]  
AM29F040B [CX0001] AM29F040B@TSOP32 [CX1002]  
AM29F040B(Reverse)@TSOP32 [CX1002] AM29F080@TSOP40 [CX1006]  
AM29F040B@PLCC32 [CX2032] AM29F080B@TSOP40 [CX1006]  
AM29F080(REVERSE)@TSOP40 [CX1006] AM29F100B@TSOP48 [CX1004]  
AM29F080@PSOP44 [CX1014] AM29F100T@TSOP48 [CX1004]  
AM29F080B@PSOP44 [CX1014] AM29F100T@PSOP44 [CX1014]  
AM29F100B(REVERSE)@TSOP48 [CX1004] AM29F160DB(REVERSE)@TSOP48 [CX1004]  
AM29F100B@PSOP44 [CX1014] AM29F160DB@TSOP48 [CX1004]  
AM29F100T(REVERSE)@TSOP48 [CX1004] AM29F160DT(REVERSE)@TSOP48 [CX1004]  
AM29F160DT@TSOP48 [CX1004] AM29F200AB(REVERSE)@TSOP48 [CX1004]  
AM29F200AB@PSOP44 [CX1014] AM29F200AB@TSOP48 [CX1004]  
AM29F200AT(REVERSE)@TSOP48 [CX1004] AM29F200AT@TSOP48 [CX1004]  
AM29F200AT@PSOP44 [CX1014] AM29F200BB(REVERSE)@TSOP48 [CX1004]  
AM29F200BB@PSOP44 [CX1014] AM29F200BB@TSOP48 [CX1004]  
AM29F200BT(REVERSE)@TSOP48 [CX1004] AM29F200BT@TSOP48 [CX1004]  
AM29F200BT@PSOP44 [CX1014] AM29F400AB(REVERSE)@TSOP48 [CX1004]  
AM29F400AB@PSOP44 [CX1014] AM29F400AB@TSOP48 [CX1004]  
AM29F400AT(REVERSE)@TSOP48 [CX1004] AM29F400AT@TSOP48 [CX1004]  
AM29F400AT@PSOP44 [CX1014]

AM29F400BB(REVERSE)@TSOP48 [CX1004]  
AM29F400BB@PSOP44 [CX1014] AM29F400BB@TSOP48 [CX1004]  
AM29F400BT(REVERSE)@TSOP48 [CX1004]  
AM29F400BT@PSOP44 [CX1014] AM29F400BT@TSOP48 [CX1004]  
AM29F800B(REVERSE)@TSOP48 [CX1004]  
AM29F800B@PSOP44 [CX1014] AM29F800B@TSOP48 [CX1004]  
AM29F800BB(REVERSE)@TSOP48 [CX1004]  
AM29F800BB@FBGA48 [CX5039] AM29F800BB@PSOP44 [CX1014]  
AM29F800BB@TSOP48 [CX1004]  
AM29F800BT(REVERSE)@TSOP48 [CX1004]  
AM29F800BT@FBGA48 [CX5039] AM29F800BT@PSOP44 [CX1014]  
AM29F800BT@TSOP48 [CX1004]  
AM29F800T(REVERSE)@TSOP48 [CX1004]  
AM29F800T@PSOP44 [CX1014] AM29F800T@TSOP48 [CX1004]  
AM29LL800B@TSOP48 [CX1004] AM29LL800BB@TSOP48 [CX1004]  
AM29LL800BT@TSOP48 [CX1004] AM29LL800T@TSOP48 [CX1004]  
AM29LV001BB(REVERSE)@TSOP32 [CX1002]  
AM29LV001BB@PLCC32 [CX2032] AM29LV001BB@TSOP32 [CX1002]  
AM29LV001BT(REVERSE)@TSOP32 [CX1002]  
AM29LV001BT@PLCC32 [CX2032] AM29LV001BT@TSOP32 [CX1002]  
AM29LV002@TSOP40 [CX1006] AM29LV002B@TSOP40 [CX1006]  
AM29LV002BB@TSOP40 [CX1006] AM29LV002BT@TSOP40 [CX1006]  
AM29LV004B@TSOP40 [CX1006] AM29LV004BB@TSOP40 [CX1006]  
AM29LV004BT@TSOP40 [CX1006] AM29LV004T@TSOP40 [CX1006]  
AM29LV008B@TSOP40 [CX1006] AM29LV008BB@TSOP40 [CX1006]  
AM29LV008BT@TSOP40 [CX1006] AM29LV008T@TSOP40 [CX1006]  
AM29LV017B(REVERSE)@TSOP40 [CX1006]  
AM29LV017B@FBGA48 [CX5022] AM29LV017B@TSOP40 [CX1006]  
AM29LV017D(REVERSE)@TSOP40 [CX1006]  
AM29LV017D@FBGA48 [CX5022] AM29LV017D@TSOP40 [CX1006]  
AM29LV033C@TSOP40 [CX1006] AM29LV033MU@FBGA48 [CX5022]  
AM29LV033MU@TSOP40 [CX1006] AM29LV065D@FBGA63 [CX5041]  
AM29LV065D@TSOP48 [CX1004] AM29LV065MU@FBGA63 [CX5041]  
AM29LV065MU@TSOP48 [CX1004] AM29LV080@TSOP40 [CX1006]  
AM29LV081@TSOP40 [CX1006] AM29LV081B@TSOP40 [CX1006]  
AM29LV116BB@TSOP40 [CX1006] AM29LV116BT@TSOP40 [CX1006]  
AM29LV116DB@TSOP40 [CX1006] AM29LV116DT@TSOP40 [CX1006]  
AM29LV128MH(REVERSE)@TSOP56 [CX1011]  
AM29LV128MH@FBGA64 [CX5074] AM29LV128MH@TSOP56 [CX1011]  
AM29LV128ML(REVERSE)@TSOP56 [CX1011]  
AM29LV128ML@FBGA64 [CX5074] AM29LV128ML@TSOP56 [CX1011]  
AM29LV160BB(REVERSE)@TSOP48 [CX1004]  
AM29LV160BB@FBGA48 [CX5022] AM29LV160BB@PSOP44 [CX1014]  
AM29LV160BB@TSOP48 [CX1004]  
AM29LV160BT(REVERSE)@TSOP48 [CX1004]  
AM29LV160BT@FBGA48 [CX5022] AM29LV160BT@PSOP44 [CX1014]  
AM29LV160BT@TSOP48 [CX1004]  
AM29LV160DB(REVERSE)@TSOP48 [CX1004]  
AM29LV160DB@FBGA48 [CX5022] AM29LV160DB@PSOP44 [CX1014]  
AM29LV160DB@TSOP48 [CX1004]  
AM29LV160DT(REVERSE)@TSOP48 [CX1004]  
AM29LV160DT@FBGA48 [CX5022] AM29LV160DT@PSOP44 [CX1014]  
AM29LV160DT@TSOP48 [CX1004] AM29LV160MA@PSOP44 [CX1014]  
AM29LV160MB(REVERSE)@TSOP48 [CX1004]  
AM29LV160MB@FBGA48 [CX5022] AM29LV160MB@FBGA64 [CX5074]  
AM29LV160MB@PSOP44 [CX1014] AM29LV160MB@TSOP48 [CX1004]  
AM29LV160MT(REVERSE)@TSOP48 [CX1004]  
AM29LV160MT@FBGA48 [CX5022] AM29LV160MT@FBGA64 [CX5074]  
AM29LV160MT@PSOP44 [CX1014] AM29LV160MT@TSOP48 [CX1004]

AM29LV200B(REVERSE)@TSOP48 [CX1004]  
AM29LV200B@PSOP44 [CX1014] AM29LV200B@TSOP48 [CX1004]  
AM29LV200BB(REVERSE)@TSOP48 [CX1004]  
AM29LV200BB@FBGA48 [CX5002] AM29LV200BB@PSOP44 [CX1014]  
AM29LV200BB@TSOP48 [CX1004]  
AM29LV200BT(REVERSE)@TSOP48 [CX1004]  
AM29LV200BT@FBGA48 [CX5002] AM29LV200BT@PSOP44 [CX1014]  
AM29LV200BT@TSOP48 [CX1004]  
AM29LV200T(REVERSE)@TSOP48 [CX1004]  
AM29LV200T@PSOP44 [CX1014] AM29LV200T@TSOP48 [CX1004]  
AM29LV256MH(REVERSE)@TSOP56 [CX1011]  
AM29LV256MH@FBGA64 [CX5075] AM29LV256MH@TSOP56 [CX1011]  
AM29LV256ML(REVERSE)@TSOP56 [CX1011]  
AM29LV256ML@FBGA64 [CX5075] AM29LV256ML@TSOP56 [CX1011]  
AM29LV320DB@FBGA48 [CX5040] AM29LV320DB@TSOP48 [CX1004]  
AM29LV320DT@FBGA48 [CX5040] AM29LV320DT@TSOP48 [CX1004]  
AM29LV320FB@TSOP48 [CX1004] AM29LV320FT@TSOP48 [CX1004]  
AM29LV320MB@FBGA48 [CX5022] AM29LV320MB@FBGA64 [CX5074]  
AM29LV320MB@TSOP48 [CX1004]  
AM29LV320MH(REVERSE)@TSOP56 [CX1011]  
AM29LV320MH@FBGA64 [CX5074] AM29LV320MH@TSOP56 [CX1011]  
AM29LV320ML(REVERSE)@TSOP56 [CX1011]  
AM29LV320ML@FBGA64 [CX5074] AM29LV320ML@TSOP56 [CX1011]  
AM29LV320MT@FBGA48 [CX5022] AM29LV320MT@FBGA64 [CX5074]  
AM29LV320MT@TSOP48 [CX1004]  
AM29LV400B(REVERSE)@TSOP48 [CX1004]  
AM29LV400B@FBGA48 [CX5002] AM29LV400B@PSOP44 [CX1014]  
AM29LV400B@TSOP48 [CX1004]  
AM29LV400BB(REVERSE)@TSOP48 [CX1004]  
AM29LV400BB@FBGA48 [CX5002] AM29LV400BB@PSOP44 [CX1014]  
AM29LV400BB@TSOP48 [CX1004]  
AM29LV400BT(REVERSE)@TSOP48 [CX1004]  
AM29LV400BT@FBGA48 [CX5002] AM29LV400BT@PSOP44 [CX1014]  
AM29LV400BT@TSOP48 [CX1004]  
AM29LV400T(REVERSE)@TSOP48 [CX1004]  
AM29LV400T@FBGA48 [CX5002] AM29LV400T@PSOP44 [CX1014]  
AM29LV400T@TSOP48 [CX1004] AM29LV640DH@SSOP56 [CX1029]  
AM29LV640DL@SSOP56 [CX1029] AM29LV640DU@FBGA63 [CX5041]  
AM29LV640DU@FBGA64 [CX5074] AM29LV640GU@FBGA63 [CX5041]  
AM29LV640GU@FBGA64 [CX5074] AM29LV640MB@FBGA63 [CX5041]  
AM29LV640MB@FBGA64 [CX5074] AM29LV640MB@TSOP48 [CX1004]  
AM29LV640MH(REVERSE)@TSOP56 [CX1011]  
AM29LV640MH@FBGA64 [CX5074] AM29LV640MH@TSOP56 [CX1011]  
AM29LV640ML(REVERSE)@TSOP56 [CX1011]  
AM29LV640ML@FBGA64 [CX5074] AM29LV640ML@TSOP56 [CX1011]  
AM29LV640MT@FBGA63 [CX5041] AM29LV640MT@FBGA64 [CX5074]  
AM29LV640MT@TSOP48 [CX1004] AM29LV640MU@FBGA63 [CX5041]  
AM29LV640MU@FBGA64 [CX5074]  
AM29LV641DH(REVERSE)@TSOP48 [CX1004]  
AM29LV641DH@TSOP48 [CX1004]  
AM29LV641DL(REVERSE)@TSOP48 [CX1004]  
AM29LV641DL@TSOP48 [CX1004]  
AM29LV641GH(REVERSE)@TSOP48 [CX1004]  
AM29LV641GH@TSOP48 [CX1004]  
AM29LV641GL(REVERSE)@TSOP48 [CX1004]  
AM29LV641GL@TSOP48 [CX1004]  
AM29LV641MH(REVERSE)@TSOP48 [CX1004]  
AM29LV641MH@TSOP48 [CX1004]  
AM29LV641ML(REVERSE)@TSOP48 [CX1004]

AM29LV641ML@TSOP48 [CX1004] AM29LV642D@FBGA64 [CX5074]  
AM29LV642G@FBGA64 [CX5074] AM29LV652D@FBGA63 [CX5041]  
AM29LV800B(REVERSE)@TSOP48 [CX1004]  
AM29LV800B@PSOP44 [CX1014] AM29LV800B@TSOP48 [CX1004]  
AM29LV800BB(REVERSE)@TSOP48 [CX1004]  
AM29LV800BB@FBGA48 [CX5039] AM29LV800BB@PSOP44 [CX1014]  
AM29LV800BB@TSOP48 [CX1004]  
AM29LV800BT(REVERSE)@TSOP48 [CX1004]  
AM29LV800BT@FBGA48 [CX5039] AM29LV800BT@PSOP44 [CX1014]  
AM29LV800BT@TSOP48 [CX1004]  
AM29LV800DB(REVERSE)@TSOP48 [CX1004]  
AM29LV800DB(WB)@FBGA48 [CX5039] AM29LV800DB(WC)@FBGA48 [CX5043]  
AM29LV800DB@PSOP44 [CX1014] AM29LV800DB@TSOP48 [CX1004]  
AM29LV800DT(REVERSE)@TSOP48 [CX1004]  
AM29LV800DT(WB)@FBGA48 [CX5039] AM29LV800DT(WC)@FBGA48 [CX5043]  
AM29LV800DT@PSOP44 [CX1014] AM29LV800DT@TSOP48 [CX1004]  
AM29LV800T(REVERSE)@TSOP48 [CX1004]  
AM29LV800T@PSOP44 [CX1014] AM29LV800T@TSOP48 [CX1004]  
AM29PDL128G70(REVERSE)@FBGA80 [CX5147]  
AM29PDL128G70@FBGA80 [CX5147] AM29PDL128G80@FBGA80 [CX5147]  
AM29PDL128G90@FBGA80 [CX5147] AM29PDS322DB@FBGA48 [CX50UN]  
AM29PDS322DT@FBGA48 [CX50UN] AM29PL160BB@PSOP44 [CX1014]  
AM29PL160BB@TSOP48 [CX1004] AM29PL160CB@PSOP44 [CX1014]  
AM29PL160CB@TSOP48 [CX1004] AM29PL160CT@PSOP44 [CX1014]  
AM29PL160CT@TSOP48 [CX1004] AM29SL160BB@FBGA48 [CX5022]  
AM29SL160BB@TSOP48 [CX1004] AM29SL160BT@FBGA48 [CX5022]  
AM29SL160BT@TSOP48 [CX1004] AM29SL160CB@FBGA48 [CX5022]  
AM29SL160CB@TSOP48 [CX1004] AM29SL160CT@FBGA48 [CX5022]  
AM29SL160CT@TSOP48 [CX1004] AM29SL400CB@FBGA48 [CX5002]  
AM29SL400CB@TSOP48 [CX1004] AM29SL400CT@FBGA48 [CX5002]  
AM29SL400CT@TSOP48 [CX1004]  
AM29SL800BB(REVERSE)@TSOP48 [CX1004]  
AM29SL800BB@FBGA48 [CX5039] AM29SL800BB@TSOP48 [CX1004]  
AM29SL800BT(REVERSE)@TSOP48 [CX1004]  
AM29SL800BT@FBGA48 [CX5039] AM29SL800BT@TSOP48 [CX1004]  
AM29SL800CB(REVERSE)@TSOP48 [CX1004]  
AM29SL800CB@FBGA48 [CX5039] AM29SL800CB@TSOP48 [CX1004]  
AM29SL800CT(REVERSE)@TSOP48 [CX1004]  
AM29SL800CT@FBGA48 [CX5039] AM29SL800CT@TSOP48 [CX1004]  
AM29SL800DB(REVERSE)@TSOP48 [CX1004]  
AM29SL800DB@TSOP48 [CX1004] AM29SL800DBUF@FBGA48 [CX5038]  
AM29SL800DBVG@FBGA48 [CX5038] AM29SL800DBVU@FBGA48 [CX5043]  
AM29SL800DBWA@FBGA48 [CX5002] AM29SL800DBWC@FBGA48 [CX5022]  
AM29SL800DT(REVERSE)@TSOP48 [CX1004]  
AM29SL800DT@TSOP48 [CX1004] AM29SL800DTUF@FBGA48 [CX5038]  
AM29SL800DTVG@FBGA48 [CX5038] AM29SL800DTVU@FBGA48 [CX5043]  
AM29SL800DTWA@FBGA48 [CX5002] AM29SL800DTWC@FBGA48 [CX5022]  
AT29BDS640GB73@FBGA64 [CX50UN] AT29BDS640GB74@FBGA64 [CX50UN]  
AT29BDS640GB78@FBGA64 [CX50UN] AT29BDS640GB79@FBGA64 [CX50UN]  
AT29BDS640GB93@FBGA64 [CX50UN] AT29BDS640GB94@FBGA64 [CX50UN]  
AT29BDS640GB98@FBGA64 [CX50UN] AT29BDS640GB99@FBGA64 [CX50UN]  
AT29BDS640GT73@FBGA64 [CX50UN] AT29BDS640GT74@FBGA64 [CX50UN]  
AT29BDS640GT78@FBGA64 [CX50UN] AT29BDS640GT79@FBGA64 [CX50UN]  
AT29BDS640GT93@FBGA64 [CX50UN] AT29BDS640GT94@FBGA64 [CX50UN]  
AT29BDS640GT98@FBGA64 [CX50UN] AT29BDS640GT99@FBGA64 [CX50UN]  
BS128HD5V(AM29BDS128HD)@FBGA80 [CX5053]  
BS128HD6V(AM29BDS128HD)@FBGA80 [CX5053]  
BS128HD8V(AM29BDS128HD)@FBGA80 [CX5053]  
BS128HD9V(AM29BDS128HD)@FBGA80 [CX5053]

BS128HE5V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HE6V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HE8V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HE9V(AM29BDS128HE)@FBGA80 [CX5053]  
BS128HF5V(AM29BDS128HF)@FBGA80 [CX5053]  
BS128HF6V(AM29BDS128HF)@FBGA80 [CX5053]  
BS128HF8V(AM29BDS128HF)@FBGA80 [CX5053]  
BS128HF9V(AM29BDS128HF)@FBGA80 [CX5053]  
BS640HD8V(AM29BDS640HD)@FBGA64 [CX5053]  
BS640HD9V(AM29BDS640HD)@FBGA64 [CX5053]  
BS640HE8V(AM29BDS640HE)@FBGA64 [CX5053]  
BS640HE9V(AM29BDS640HE)@FBGA64 [CX5053]  
BS640HF8V(AM29BDS640HF)@FBGA64 [CX5053]  
BS640HF9V(AM29BDS640HF)@FBGA64 [CX5053]  
DS42514(AM29DL1634DB)@FBGA69 [CX5001]  
DS42515(AM29DL1644DB)@FBGA69 [CX5001]  
DS42516(AM29DL324DB)@FBGA73 [CX5001]  
DS42546(AM29DL1634DT)@FBGA69 [CX5001]  
DS42553(AM29DL323DT)@FBGA73 [CX5001]  
DS42585(AM29DL323DT)@FBGA73 [CX5001]  
DS42587(AM29DL324DB)@FBGA73 [CX5001]  
DS42678(AM29LV320MT)@FBGA67 [CX5001]  
DS42689(AM29LV320MT)@FBGA64 [CX5004]  
DS42690(AM29LV320MB)@FBGA64 [CX5004]  
DS42695(AM29LV320MT)@FBGA64 [CX5074]  
DS42696(AM29LV320MB)@FBGA64 [CX5074]  
DS42725(AM50DL128CH)@FBGA88 [CX5001]  
M410000000(AM41DL1614DT)@FBGA69 [CX5001]  
M410000001(AM41DL1614DB)@FBGA69 [CX5001]  
M410000002(AM41DL1614DT)@FBGA69 [CX5001]  
M410000003(AM41DL1614DB)@FBGA69 [CX5001]  
M410000004(AM41DL1624DT)@FBGA69 [CX5001]  
M410000005(AM41DL1624DB)@FBGA69 [CX5001]  
M410000006(AM41DL1624DT)@FBGA69 [CX5001]  
M410000007(AM41DL1624DB)@FBGA69 [CX5001]  
M410000008(AM41DL1634DT)@FBGA69 [CX5001]  
M410000009(AM41DL1634DB)@FBGA69 [CX5001]  
M41000000A(AM41DL1634DT)@FBGA69 [CX5001]  
M41000000B(AM41DL1634DB)@FBGA69 [CX5001]  
M41000000C(AM41DL1644DT)@FBGA69 [CX5001]  
M41000000D(AM41DL1644DB)@FBGA69 [CX5001]  
M41000000E(AM41DL1644DT)@FBGA69 [CX5001]  
M41000000F(AM41DL1644DB)@FBGA69 [CX5001]  
M41000000G(AM41DL6408G)@FBGA73 [CX5001]  
M41000000H(AM41DL6408G)@FBGA73 [CX5001]  
M41000001W(AM41DL3224GT)@FBGA73 [CX5001]  
M41000001X(AM41DL3224GB)@FBGA73 [CX5001]  
M41000001Y(AM41DL3224GT)@FBGA73 [CX5001]  
M41000001Z(AM41DL3224GB)@FBGA73 [CX5001]  
M410000020(AM41DL3234GT)@FBGA73 [CX5001]  
M410000021(AM41DL3234GB)@FBGA73 [CX5001]  
M410000022(AM41DL3234GT)@FBGA73 [CX5001]  
M410000023(AM41DL3234GB)@FBGA73 [CX5001]  
M410000024(AM41DL3244GT)@FBGA73 [CX5001]  
M410000025(AM41DL3244GB)@FBGA73 [CX5001]  
M410000026(AM41DL3244GT)@FBGA73 [CX5001]  
M410000027(AM41DL3244GB)@FBGA73 [CX5001]  
M41000002L(AM41DL3228GT)@FBGA73 [CX5001]  
M41000002M(AM41DL3228GB)@FBGA73 [CX5001]



M41000002N (AM41DL3228GT)@FBGA73 [CX5001]  
M41000002O (AM41DL3228GB)@FBGA73 [CX5001]  
M41000002P (AM41DL3238GT)@FBGA73 [CX5001]  
M41000002Q (AM41DL3238GB)@FBGA73 [CX5001]  
M41000002R (AM41DL3238GT)@FBGA73 [CX5001]  
M41000002S (AM41DL3238GB)@FBGA73 [CX5001]  
M41000002T (AM41DL3248GT)@FBGA73 [CX5001]  
M41000002U (AM41DL3248GB)@FBGA73 [CX5001]  
M41000002V (AM41DL3248GT)@FBGA73 [CX5001]  
M41000002W (AM41DL3248GB)@FBGA73 [CX5001]  
M41000003D (AM41DL3208GT)@FBGA73 [CX5001]  
M41000003E (AM41DL3208GB)@FBGA73 [CX5001]  
M41000003F (AM41DL3208GT)@FBGA73 [CX5001]  
M41000003G (AM41DL3208GB)@FBGA73 [CX5001]  
M410000095 (AM41LV3204MT)@FBGA69 [CX5005]  
M410000096 (AM41LV3204MB)@FBGA69 [CX5005]  
M41000009B (AM41DL6408H)@FBGA73 [CX5001]  
M41000009C (AM41DL6408H)@FBGA73 [CX5001]  
M41000009D (AM41DL6408H)@FBGA73 [CX5001]  
M420000000 (AM42DL640AG)@FBGA73 [CX5001]  
M420000001 (AM42DL640AG)@FBGA73 [CX5001]  
M420000004 (AM42DL1642DT)@FBGA69 [CX5001]  
M420000005 (AM42DL1642DB)@FBGA69 [CX5001]  
M420000006 (AM42DL1642DT)@FBGA69 [CX5001]  
M420000007 (AM42DL1642DB)@FBGA69 [CX5001]  
M42000000I (AM42DL1612DT)@FBGA69 [CX5001]  
M42000000J (AM42DL1612DB)@FBGA69 [CX5001]  
M42000000K (AM42DL1612DT)@FBGA69 [CX5001]  
M42000000L (AM42DL1612DB)@FBGA69 [CX5001]  
M42000000M (AM42DL1622DT)@FBGA69 [CX5001]  
M42000000N (AM42DL1622DB)@FBGA69 [CX5001]  
M42000000O (AM42DL1622DT)@FBGA69 [CX5001]  
M42000000P (AM42DL1622DB)@FBGA69 [CX5001]  
M42000000Q (AM42DL1632DT)@FBGA69 [CX5001]  
M42000000R (AM42DL1632DB)@FBGA69 [CX5001]  
M42000000S (AM42DL1632DT)@FBGA69 [CX5001]  
M42000000T (AM42DL1632DB)@FBGA69 [CX5001]  
M42000000U (AM42DL1642DT)@FBGA69 [CX5001]  
M42000000V (AM42DL1642DB)@FBGA69 [CX5001]  
M42000000W (AM42DL1642DT)@FBGA69 [CX5001]  
M42000000X (AM42DL1642DB)@FBGA69 [CX5001]  
M42000001A (AM42DL1614DT)@FBGA69 [CX5001]  
M42000001B (AM42DL1614DB)@FBGA69 [CX5001]  
M42000001C (AM42DL1614DT)@FBGA69 [CX5001]  
M42000001D (AM42DL1614DB)@FBGA69 [CX5001]  
M42000001E (AM42DL1624DT)@FBGA69 [CX5001]  
M42000001F (AM42DL1624DB)@FBGA69 [CX5001]  
M42000001G (AM42DL1624DT)@FBGA69 [CX5001]  
M42000001H (AM42DL1624DB)@FBGA69 [CX5001]  
M42000001I (AM42DL1634DT)@FBGA69 [CX5001]  
M42000001J (AM42DL1634DB)@FBGA69 [CX5001]  
M42000001K (AM42DL1634DT)@FBGA69 [CX5001]  
M42000001L (AM42DL1634DB)@FBGA69 [CX5001]  
M42000001M (AM42DL1644DT)@FBGA69 [CX5001]  
M42000001N (AM42DL1644DB)@FBGA69 [CX5001]  
M42000001O (AM42DL1644DT)@FBGA69 [CX5001]  
M42000001P (AM42DL1644DB)@FBGA69 [CX5001]  
M420000022 (AM42DL3224GT)@FBGA73 [CX5001]  
M420000023 (AM42DL3224GB)@FBGA73 [CX5001]

M420000024 (AM42DL3224GT)@FBGA73 [CX5001]  
M420000025 (AM42DL3224GB)@FBGA73 [CX5001]  
M420000026 (AM42DL3234GT)@FBGA73 [CX5001]  
M420000027 (AM42DL3234GB)@FBGA73 [CX5001]  
M420000028 (AM42DL3234GT)@FBGA73 [CX5001]  
M420000029 (AM42DL3234GB)@FBGA73 [CX5001]  
M42000002A (AM42DL3244GT)@FBGA73 [CX5001]  
M42000002B (AM42DL3244GB)@FBGA73 [CX5001]  
M42000002C (AM42DL3244GT)@FBGA73 [CX5001]  
M42000002D (AM42DL3244GB)@FBGA73 [CX5001]  
M42000002U (AM42DL6404G)@FBGA73 [CX5001]  
M42000002V (AM42DL6404G)@FBGA73 [CX5001]  
M42000005M (AM42DL6402G)@FBGA73 [CX5001]  
M42000005N (AM42DL6402G)@FBGA73 [CX5001]  
M42000005W (AM42DL3224GT)@FBGA73 [CX5001]  
M42000005X (AM42DL3224GB)@FBGA73 [CX5001]  
M42000005Y (AM42DL3234GT)@FBGA73 [CX5001]  
M42000005Z (AM42DL3234GB)@FBGA73 [CX5001]  
M420000060 (AM42DL3244GT)@FBGA73 [CX5001]  
M420000061 (AM42DL3244GB)@FBGA73 [CX5001]  
M420000078 (AM42DL640AH)@FBGA73 [CX5001]  
M420000079 (AM42DL640AH)@FBGA73 [CX5001]  
M450000000 (AM45DL6408G)@FBGA73 [CX5001]  
M450000001 (AM45DL6408G)@FBGA73 [CX5001]  
M450000008 (AM45DL3208GT)@FBGA73 [CX5001]  
M450000009 (AM45DL3208GB)@FBGA73 [CX5001]  
M45000000A (AM45DL3208GT)@FBGA73 [CX5001]  
M45000000B (AM45DL3208GB)@FBGA73 [CX5001]  
M45000000S (AM45DL3228GT)@FBGA73 [CX5001]  
M45000000T (AM45DL3228GB)@FBGA73 [CX5001]  
M45000000U (AM45DL3228GT)@FBGA73 [CX5001]  
M45000000V (AM45DL3228GB)@FBGA73 [CX5001]  
M45000001C (AM45DL3238GT)@FBGA73 [CX5001]  
M45000001D (AM45DL3238GB)@FBGA73 [CX5001]  
M45000001E (AM45DL3238GT)@FBGA73 [CX5001]  
M45000001F (AM45DL3238GB)@FBGA73 [CX5001]  
M45000001W (AM45DL3248GT)@FBGA73 [CX5001]  
M45000001X (AM45DL3248GB)@FBGA73 [CX5001]  
M45000001Y (AM45DL3248GT)@FBGA73 [CX5001]  
M45000001Z (AM45DL3248GB)@FBGA73 [CX5001]  
M490000000 (AM49DL640BG)@FBGA73 [CX5001]  
M490000001 (AM49DL640BG)@FBGA73 [CX5001]  
M49000000G (AM49DL320BGT)@FBGA73 [CX5001]  
M49000000H (AM49DL320BGT)@FBGA73 [CX5001]  
M49000000J (AM49DL322BGT)@FBGA73 [CX5001]  
M49000000K (AM49DL322BGT)@FBGA73 [CX5001]  
M49000000L (AM49DL322BGB)@FBGA73 [CX5001]  
M49000000M (AM49DL322BGB)@FBGA73 [CX5001]  
M49000000N (AM49DL323BGT)@FBGA73 [CX5001]  
M49000000O (AM49DL323BGT)@FBGA73 [CX5001]  
M49000000P (AM49DL323BGB)@FBGA73 [CX5001]  
M49000000Q (AM49DL323BGB)@FBGA73 [CX5001]  
M49000000R (AM49DL324BGT)@FBGA73 [CX5001]  
M49000000S (AM49DL324BGT)@FBGA73 [CX5001]  
M49000000T (AM49DL324BGB)@FBGA73 [CX5001]  
M49000000U (AM49DL324BGB)@FBGA73 [CX5001]  
M49000001A (AM49DL320BGB)@FBGA73 [CX5001]  
M49000001B (AM49DL320BGB)@FBGA73 [CX5001]  
M49000001Y (AM49PDL640AG)@FBGA73 [CX5072]

M49000001Z (AM49PDL640AG)@FBGA73 [CX5072]  
M490000025 (AM49DL640AG)@FBGA73 [CX5001]  
M490000026 (AM49DL640AG)@FBGA73 [CX5001]  
M490000028 (AM49PDL127BH)@FBGA73 [CX5001]  
M490000029 (AM49PDL127BH)@FBGA73 [CX5001]  
M49000002I (AM49PDL127AH)@FBGA73 [CX5001]  
M49000002J (AM49PDL127AH)@FBGA73 [CX5001]  
M49000002T (AM49LV6408MT)@FBGA69 [CX5005]  
M49000002U (AM49LV6408MB)@FBGA69 [CX5005]  
M49000002V (AM49LV6408MT)@FBGA69 [CX5005]  
M49000002X (AM49LV6408MB)@FBGA69 [CX5005]  
M490000030 (AM49PDL129BH)@FBGA73 [CX5001]  
M490000031 (AM49PDL129BH)@FBGA73 [CX5001]  
M490000032 (AM49DL3208GB)@FBGA69 [CX5001]  
M490000032 (AM49DL3208GT)@FBGA69 [CX5005]  
M490000034 (AM49DL3208GT)@FBGA69 [CX5005]  
M490000035 (AM49DL3208GB)@FBGA69 [CX5001]  
M49000003A (AM49DL640BH)@FBGA73 [CX5001]  
M49000003B (AM49DL640BH)@FBGA73 [CX5001]  
M49000003C (AM49DL640BH)@FBGA73 [CX5001]  
M49000003D (AM49DL640AH)@FBGA73 [CX5001]  
M49000003E (AM49DL640AH)@FBGA73 [CX5001]  
M49000003F (AM49DL6408H)@FBGA73 [CX5001]  
M49000003G (AM49DL6408H)@FBGA73 [CX5001]  
M49000003H (AM49DL6408H)@FBGA73 [CX5001]  
M49000003I (AM49DL6408H)@FBGA73 [CX5001]  
M49000003J (AM49DL640AH)@FBGA73 [CX5001]  
M49000003X (AM49DL6408H)@FBGA73 [CX5001]  
M49000003Y (AM49DL6408H)@FBGA73 [CX5001]  
M49000003Z (AM49LV6408MT)@FBGA69 [CX5005]  
M49000004A (AM49LV6408MB)@FBGA69 [CX5005]  
M49000004H (AM49LV128BMH)@FBGA64 [CX5054]  
M49000004J (AM49LV128BML)@FBGA64 [CX5054]  
M49000004K (AM49LV128BMH)@FBGA64 [CX5054]  
M49000004L (AM49LV128BML)@FBGA64 [CX5054]  
M49000004S (AM49LV128BMaH)@FBGA64 [CX5054]  
M49000004T (AM49LV128BMaL)@FBGA64 [CX5054]  
M49000004U (AM49LV128BMaH)@FBGA64 [CX5054]  
M49000004V (AM49LV128BMaL)@FBGA64 [CX5054]  
M4900000K (AM49PDL129AH)@FBGA73 [CX5001]  
M4900000L (AM49PDL129AH)@FBGA73 [CX5001]  
M500000000 (AM50DL128BG)@FBGA73 [CX5001]  
M500000001 (AM50DL128BG)@FBGA73 [CX5001]  
M500000008 (AM50DL128CG)@FBGA88 [CX5001]  
M500000009 (AM50DL128CG)@FBGA88 [CX5001]  
M50000004J (AM50DL128BH)@FBGA73 [CX5001]  
M50000004K (AM50DL128BH)@FBGA73 [CX5001]  
M50000004L (AM50DL128BH)@FBGA73 [CX5001]  
M50000004M (AM50DL128CH)@FBGA88 [CX5001]  
M50000004N (AM50DL128CH)@FBGA88 [CX5001]  
M50000004P (AM50DL128CH)@FBGA88 [CX5001]  
M550000000 (AM55DL128C8G)@FBGA93 [CX5028]  
M550000001 (AM55DL128C8G)@FBGA93 [CX5028]  
MB84VD21081@FBGA61 [CX5048] MB84VD21081EA@FBGA56 [CX5045]  
MB84VD21081EM@FBGA56 [CX5045] MB84VD21082@FBGA61 [CX5048]  
MB84VD21082EA@FBGA56 [CX5045] MB84VD21082EM@FBGA56 [CX5045]  
MB84VD21083@FBGA61 [CX5048] MB84VD21083EA@FBGA56 [CX5045]  
MB84VD21083EM@FBGA56 [CX5045] MB84VD21084@FBGA61 [CX5048]  
MB84VD21084EA@FBGA56 [CX5045] MB84VD21084EM@FBGA56 [CX5045]

MB84VD21091@FBGA61 [CX5048] MB84VD21091EA@FBGA56 [CX5045]  
MB84VD21091EM@FBGA56 [CX5045] MB84VD21092@FBGA61 [CX5048]  
MB84VD21092EA@FBGA56 [CX5045] MB84VD21092EM@FBGA56 [CX5045]  
MB84VD21093@FBGA61 [CX5048] MB84VD21093EA@FBGA56 [CX5045]  
MB84VD21093EM@FBGA56 [CX5045] MB84VD21094@FBGA61 [CX5048]  
MB84VD21094EA@FBGA56 [CX5045] MB84VD21094EM@FBGA56 [CX5045]  
MB84VD21181DA@FBGA69 [CX5001] MB84VD21181EG@FBGA56 [CX5045]  
MB84VD21181EM@FBGA56 [CX5045] MB84VD21182DA@FBGA69 [CX5001]  
MB84VD21182EG@FBGA56 [CX5045] MB84VD21182EM@FBGA56 [CX5045]  
MB84VD21183DA@FBGA69 [CX5001] MB84VD21183EG@FBGA56 [CX5045]  
MB84VD21183EM@FBGA56 [CX5045] MB84VD21184DA@FBGA69 [CX5001]  
MB84VD21184EG@FBGA56 [CX5045] MB84VD21184EM@FBGA56 [CX5045]  
MB84VD21191DA@FBGA69 [CX5001] MB84VD21191EG@FBGA56 [CX5045]  
MB84VD21191EM@FBGA56 [CX5045] MB84VD21192DA@FBGA69 [CX5001]  
MB84VD21192EG@FBGA56 [CX5045] MB84VD21192EM@FBGA56 [CX5045]  
MB84VD21193DA@FBGA69 [CX5001] MB84VD21193EG@FBGA56 [CX5045]  
MB84VD21193EM@FBGA56 [CX5045] MB84VD21194DA@FBGA69 [CX5001]  
MB84VD21194EG@FBGA56 [CX5045] MB84VD21194EM@FBGA56 [CX5045]  
MB84VD22180FA@FBGA59 [CX5045] MB84VD22180FM@FBGA59 [CX5045]  
MB84VD22181EB@FBGA73 [CX5001] MB84VD22181EC@FBGA73 [CX5001]  
MB84VD22181EE@FBGA73 [CX5001] MB84VD22181FM@FBGA56 [CX5045]  
MB84VD22182EB@FBGA73 [CX5001] MB84VD22182EC@FBGA73 [CX5001]  
MB84VD22182EE@FBGA73 [CX5001] MB84VD22183EB@FBGA73 [CX5001]  
MB84VD22183EC@FBGA73 [CX5001] MB84VD22183EE@FBGA73 [CX5001]  
MB84VD22184EB@FBGA73 [CX5001] MB84VD22184EC@FBGA73 [CX5001]  
MB84VD22184EE@FBGA73 [CX5001] MB84VD22184FM@FBGA56 [CX5045]  
MB84VD22190FA@FBGA59 [CX5045] MB84VD22190FM@FBGA59 [CX5045]  
MB84VD22191EB@FBGA73 [CX5001] MB84VD22191EC@FBGA73 [CX5001]  
MB84VD22191EE@FBGA73 [CX5001] MB84VD22191FM@FBGA56 [CX5045]  
MB84VD22192EB@FBGA73 [CX5001] MB84VD22192EC@FBGA73 [CX5001]  
MB84VD22192EE@FBGA73 [CX5001] MB84VD22193EB@FBGA73 [CX5001]  
MB84VD22193EC@FBGA73 [CX5001] MB84VD22193EE@FBGA73 [CX5001]  
MB84VD22194EB@FBGA73 [CX5001] MB84VD22194EC@FBGA73 [CX5001]  
MB84VD22194EE@FBGA73 [CX5001] MB84VD22194FM@FBGA56 [CX5045]  
MB84VD22280FA@FBGA59 [CX5045] MB84VD22280FE@FBGA59 [CX5045]  
MB84VD22282EA@FBGA71 [CX5001] MB84VD22282EE@FBGA71 [CX5001]  
MB84VD22283EA@FBGA71 [CX5001] MB84VD22283EE@FBGA71 [CX5001]  
MB84VD22284EA@FBGA71 [CX5001] MB84VD22284EE@FBGA71 [CX5001]  
MB84VD22290FA@FBGA59 [CX5045] MB84VD22290FE@FBGA59 [CX5045]  
MB84VD22292EA@FBGA71 [CX5001] MB84VD22292EE@FBGA71 [CX5001]  
MB84VD22293EA@FBGA71 [CX5001] MB84VD22293EE@FBGA71 [CX5001]  
MB84VD22294EA@FBGA71 [CX5001] MB84VD22294EE@FBGA71 [CX5001]  
MB84VD22386EJ@FBGA71 [CX5001] MB84VD22387EJ@FBGA71 [CX5001]  
MB84VD22388EJ@FBGA71 [CX5001] MB84VD22396EJ@FBGA71 [CX5001]  
MB84VD22397EJ@FBGA71 [CX5001] MB84VD22398EJ@FBGA71 [CX5001]  
MB84VD23180FM@FBGA73 [CX5001] MB84VD23280FA@FBGA65 [CX5048]  
MB84VD23381FJ@FBGA65 [CX5048] MB84VD23381HJ@FBGA56 [CX5045]  
MB84VD23481FJ@FBGA65 [CX5048] MB84VD23581FJ@FBGA65 [CX5048]  
MB84VP23481FK@FBGA65 [CX5048]  
MBM29DL161BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL161BD@FBGA48 [CX5002] MBM29DL161BD@TSOP48 [CX1004]  
MBM29DL161BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL161BE@FBGA48 [CX5002] MBM29DL161BE@TSOP48 [CX1004]  
MBM29DL161TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL161TD@FBGA48 [CX5002] MBM29DL161TD@TSOP48 [CX1004]  
MBM29DL161TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL161TE@FBGA48 [CX5002] MBM29DL161TE@TSOP48 [CX1004]  
MBM29DL162BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL162BD@FBGA48 [CX5002] MBM29DL162BD@TSOP48 [CX1004]

MBM29DL162BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL162BE@FBGA48 [CX5002] MBM29DL162BE@TSOP48 [CX1004]  
MBM29DL162TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL162TD@FBGA48 [CX5002] MBM29DL162TD@TSOP48 [CX1004]  
MBM29DL162TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL162TE@FBGA48 [CX5002] MBM29DL162TE@TSOP48 [CX1004]  
MBM29DL163BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL163BD@FBGA48 [CX5002] MBM29DL163BD@TSOP48 [CX1004]  
MBM29DL163BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL163BE@FBGA48 [CX5002] MBM29DL163BE@TSOP48 [CX1004]  
MBM29DL163TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL163TD@FBGA48 [CX5002] MBM29DL163TD@TSOP48 [CX1004]  
MBM29DL163TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL163TE@FBGA48 [CX5002] MBM29DL163TE@TSOP48 [CX1004]  
MBM29DL164BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL164BD@FBGA48 [CX5002] MBM29DL164BD@TSOP48 [CX1004]  
MBM29DL164BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL164BE@FBGA48 [CX5002] MBM29DL164BE@TSOP48 [CX1004]  
MBM29DL164TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL164TD@FBGA48 [CX5002] MBM29DL164TD@TSOP48 [CX1004]  
MBM29DL164TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL164TE@FBGA48 [CX5002] MBM29DL164TE@TSOP48 [CX1004]  
MBM29DL320BF@FBGA48 [CX5039] MBM29DL320BF@TSOP48 [CX1004]  
MBM29DL320TF@FBGA48 [CX5039] MBM29DL320TF@TSOP48 [CX1004]  
MBM29DL321BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL321BD@FBGA63 [CX5047] MBM29DL321BD@TSOP48 [CX1004]  
MBM29DL321BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL321BE@FBGA63 [CX5047] MBM29DL321BE@TSOP48 [CX1004]  
MBM29DL321TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL321TD@FBGA63 [CX5047] MBM29DL321TD@TSOP48 [CX1004]  
MBM29DL321TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL321TE@FBGA63 [CX5047] MBM29DL321TE@TSOP48 [CX1004]  
MBM29DL322BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL322BD@FBGA63 [CX5047] MBM29DL322BD@TSOP48 [CX1004]  
MBM29DL322BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL322BE@FBGA63 [CX5047] MBM29DL322BE@TSOP48 [CX1004]  
MBM29DL322TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL322TD@FBGA63 [CX5047] MBM29DL322TD@TSOP48 [CX1004]  
MBM29DL322TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL322TE@FBGA63 [CX5047] MBM29DL322TE@TSOP48 [CX1004]  
MBM29DL323BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL323BD@FBGA63 [CX5047] MBM29DL323BD@TSOP48 [CX1004]  
MBM29DL323BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL323BE@FBGA63 [CX5047] MBM29DL323BE@TSOP48 [CX1004]  
MBM29DL323BF@FBGA48 [CX5039] MBM29DL323BF@TSOP48 [CX1004]  
MBM29DL323TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL323TD@FBGA63 [CX5047] MBM29DL323TD@TSOP48 [CX1004]  
MBM29DL323TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL323TE@FBGA63 [CX5047] MBM29DL323TE@TSOP48 [CX1004]  
MBM29DL323TF@FBGA48 [CX5039] MBM29DL323TF@TSOP48 [CX1004]  
MBM29DL324BD (REVERSE)@TSOP48 [CX1004]  
MBM29DL324BD@FBGA63 [CX5047] MBM29DL324BD@TSOP48 [CX1004]  
MBM29DL324BE (REVERSE)@TSOP48 [CX1004]  
MBM29DL324BE@FBGA63 [CX5047] MBM29DL324BE@TSOP48 [CX1004]  
MBM29DL324TD (REVERSE)@TSOP48 [CX1004]  
MBM29DL324TD@FBGA63 [CX5047] MBM29DL324TD@TSOP48 [CX1004]  
MBM29DL324TE (REVERSE)@TSOP48 [CX1004]  
MBM29DL324TE@FBGA63 [CX5047] MBM29DL324TE@TSOP48 [CX1004]  
MBM29DL32BF@FBGA48 [CX5039] MBM29DL32BF@TSOP48 [CX1004]

MBM29DL32TF@FBGA48 [CX5039] MBM29DL32TF@TSOP48 [CX1004]  
MBM29DL34BF@FBGA48 [CX5039] MBM29DL34BF@TSOP48 [CX1004]  
MBM29DL34TF@FBGA48 [CX5039] MBM29DL34TF@TSOP48 [CX1004]  
MBM29DL400BB@PSOP44 [CX1014] MBM29DL400BB@TSOP48 [CX1004]  
MBM29DL400BC(REVERSE)@TSOP48 [CX1004]  
MBM29DL400BC@PSOP44 [CX1014] MBM29DL400BC@TSOP48 [CX1004]  
MBM29DL400BT@PSOP44 [CX1014] MBM29DL400BT@TSOP48 [CX1004]  
MBM29DL400TC(REVERSE)@TSOP48 [CX1004]  
MBM29DL400TC@PSOP44 [CX1014] MBM29DL400TC@TSOP48 [CX1004]  
MBM29DL640E(REVERSE)@TSOP48 [CX1004]  
MBM29DL640E@FBGA63 [CX5041] MBM29DL640E@TSOP48 [CX1004]  
MBM29DL64DF@FBGA48 [CX5022] MBM29DL64DF@TSOP48 [CX1004]  
MBM29DL800B@PSOP44 [CX1014] MBM29DL800B@TSOP48 [CX1004]  
MBM29DL800BA(REVERSE)@TSOP48 [CX1004]  
MBM29DL800BA@FBGA48 [CX5039] MBM29DL800BA@PSOP44 [CX1014]  
MBM29DL800BA@TSOP48 [CX1004] MBM29DL800BB@PSOP44 [CX1014]  
MBM29DL800BB@TSOP48 [CX1004] MBM29DL800BT@PSOP44 [CX1014]  
MBM29DL800BT@TSOP48 [CX1004] MBM29DL800T@PSOP44 [CX1014]  
MBM29DL800T@TSOP48 [CX1004]  
MBM29DL800TA(REVERSE)@TSOP48 [CX1004]  
MBM29DL800TA@FBGA48 [CX5039] MBM29DL800TA@PSOP44 [CX1014]  
MBM29DL800TA@TSOP48 [CX1004] MBM29DS163BE@FBGA48 [CX5043]  
MBM29DS163BE@TSOP48 [CX1004] MBM29DS163TE@FBGA48 [CX5043]  
MBM29DS163TE@TSOP48 [CX1004] MBM29F001B [CX0001]  
MBM29F001B@PLCC32 [CX2032] MBM29F001B@TSOP32 [CX1002]  
MBM29F001T [CX0001] MBM29F001T@PLCC32 [CX2032]  
MBM29F001T@TSOP32 [CX1002] MBM29F002B [CX0001]  
MBM29F002B@PLCC32 [CX2032] MBM29F002B@TSOP32 [CX1002]  
MBM29F002NB [CX0001] MBM29F002NB@PLCC32 [CX2032]  
MBM29F002NB@TSOP32 [CX1002] MBM29F002NT [CX0001]  
MBM29F002NT@PLCC32 [CX2032] MBM29F002NT@TSOP32 [CX1002]  
MBM29F002T [CX0001] MBM29F002T@PLCC32 [CX2032]  
MBM29F002T@TSOP32 [CX1002] MBM29F010 [CX0001]  
MBM29F010@PLCC32 [CX2032] MBM29F010@TSOP32 [CX1002]  
MBM29F010A [CX0001] MBM29F010A@PLCC32 [CX2032]  
MBM29F010A@TSOP32 [CX1002] MBM29F016@PSOP44 [CX1014]  
MBM29F016@TSOP40 [CX1006] MBM29F016@TSOP48 [CX1004]  
MBM29F016A@PSOP44 [CX1014] MBM29F016A@TSOP40 [CX1006]  
MBM29F016A@TSOP48 [CX1004] MBM29F016B@PSOP44 [CX1014]  
MBM29F016B@TSOP40 [CX1006] MBM29F016B@TSOP48 [CX1004]  
MBM29F017A(REVERSE)@TSOP48 [CX1004]  
MBM29F017A@TSOP48 [CX1004] MBM29F017B@TSOP48 [CX1004]  
MBM29F017D@TSOP40 [CX1006] MBM29F017D@TSOP48 [CX1004]  
MBM29F032B@PSOP44 [CX1014] MBM29F032B@TSOP40 [CX1006]  
MBM29F033C@TSOP40 [CX1006] MBM29F040 [CX0001]  
MBM29F040@PLCC32 [CX2032] MBM29F040@TSOP32 [CX1002]  
MBM29F040B [CX0001] MBM29F040B@PLCC32 [CX2032]  
MBM29F040B@TSOP32 [CX1002] MBM29F040C@PLCC32 [CX2032]  
MBM29F040C@TSOP32 [CX1002] MBM29F080@PSOP44 [CX1014]  
MBM29F080@TSOP40 [CX1006]  
MBM29F080A(REVERSE)@TSOP40 [CX1006]  
MBM29F080A(REVERSE)@TSOP48 [CX1004]  
MBM29F080A@PSOP44 [CX1014] MBM29F080A@TSOP40 [CX1006]  
MBM29F080A@TSOP48 [CX1004] MBM29F080B@PSOP44 [CX1014]  
MBM29F080B@TSOP40 [CX1006] MBM29F100B@PSOP44 [CX1014]  
MBM29F100B@TSOP48 [CX1004] MBM29F100T@PSOP44 [CX1014]  
MBM29F100T@TSOP48 [CX1004]  
MBM29F160BE(REVERSE)@TSOP48 [CX1004]  
MBM29F160BE@TSOP48 [CX1004]

MBM29F160TE(REVERSE)@TSOP48 [CX1004]  
MBM29F160TE@TSOP48 [CX1004] MBM29F200AB@PSOP44 [CX1014]  
MBM29F200AB@TSOP48 [CX1004] MBM29F200AT@PSOP44 [CX1014]  
MBM29F200AT@TSOP48 [CX1004] MBM29F200B@PSOP44 [CX1014]  
MBM29F200B@TSOP48 [CX1004]  
MBM29F200BC(REVERSE)@TSOP48 [CX1004]  
MBM29F200BC@PSOP44 [CX1014] MBM29F200BC@TSOP48 [CX1004]  
MBM29F200T@PSOP44 [CX1014] MBM29F200T@TSOP48 [CX1004]  
MBM29F200TC(REVERSE)@TSOP48 [CX1004]  
MBM29F200TC@PSOP44 [CX1014] MBM29F200TC@TSOP48 [CX1004]  
MBM29F400AB@PSOP44 [CX1014] MBM29F400AB@TSOP48 [CX1004]  
MBM29F400AT@PSOP44 [CX1014] MBM29F400AT@TSOP48 [CX1004]  
MBM29F400B@PSOP44 [CX1014] MBM29F400B@TSOP48 [CX1004]  
MBM29F400BB@PSOP44 [CX1014] MBM29F400BB@TSOP48 [CX1004]  
MBM29F400BC(REVERSE)@TSOP48 [CX1004]  
MBM29F400BC@PSOP44 [CX1014] MBM29F400BC@TSOP48 [CX1004]  
MBM29F400BT@PSOP44 [CX1014] MBM29F400BT@TSOP48 [CX1004]  
MBM29F400T@PSOP44 [CX1014] MBM29F400T@TSOP48 [CX1004]  
MBM29F400TC(REVERSE)@TSOP48 [CX1004]  
MBM29F400TC@PSOP44 [CX1014] MBM29F400TC@TSOP48 [CX1004]  
MBM29F800B@PSOP44 [CX1014] MBM29F800B@TSOP48 [CX1004]  
MBM29F800BA(REVERSE)@TSOP48 [CX1004]  
MBM29F800BA@PSOP44 [CX1014] MBM29F800BA@TSOP48 [CX1004]  
MBM29F800BB@PSOP44 [CX1014] MBM29F800BB@TSOP48 [CX1004]  
MBM29F800BT@PSOP44 [CX1014] MBM29F800BT@TSOP48 [CX1004]  
MBM29F800T@PSOP44 [CX1014] MBM29F800T@TSOP48 [CX1004]  
MBM29F800TA(REVERSE)@TSOP48 [CX1004]  
MBM29F800TA@PSOP44 [CX1014] MBM29F800TA@TSOP48 [CX1004]  
MBM29LL800B@TSOP48 [CX1004] MBM29LL800BB@TSOP48 [CX1004]  
MBM29LL800BT@TSOP48 [CX1004] MBM29LL800T@TSOP48 [CX1004]  
MBM29LV001B@PLCC32 [CX2032]  
MBM29LV001BB(REVERSE)@TSOP32 [CX1002]  
MBM29LV001BB@PLCC32 [CX2032] MBM29LV001BB@TSOP32 [CX1002]  
MBM29LV001BC(REVERSE)@TSOP32 [CX1002]  
MBM29LV001BC@PLCC32 [CX2032] MBM29LV001BC@TSOP32 [CX1002]  
MBM29LV001BT(REVERSE)@TSOP32 [CX1002]  
MBM29LV001BT@PLCC32 [CX2032] MBM29LV001BT@TSOP32 [CX1002]  
MBM29LV001T@TSOP32 [CX1002]  
MBM29LV001TC(REVERSE)@TSOP32 [CX1002]  
MBM29LV001TC@PLCC32 [CX2032] MBM29LV001TC@TSOP32 [CX1002]  
MBM29LV002B@TSOP40 [CX1006] MBM29LV002T@TSOP40 [CX1006]  
MBM29LV004B@TSOP40 [CX1006] MBM29LV004BB@TSOP40 [CX1006]  
MBM29LV004BT@TSOP40 [CX1006] MBM29LV004T@TSOP40 [CX1006]  
MBM29LV008B@TSOP40 [CX1006] MBM29LV008BB@TSOP40 [CX1006]  
MBM29LV008BT@TSOP40 [CX1006] MBM29LV008T@TSOP40 [CX1006]  
MBM29LV016/B@TSOP40 [CX1006] MBM29LV016/T@TSOP40 [CX1006]  
MBM29LV016B@TSOP40 [CX1006] MBM29LV017@FBGA48 [CX5022]  
MBM29LV017@TSOP40 [CX1006] MBM29LV017B@TSOP40 [CX1006]  
MBM29LV017E@TSOP40 [CX1006] MBM29LV033C@TSOP40 [CX1006]  
MBM29LV080@TSOP40 [CX1006] MBM29LV080A@TSOP40 [CX1006]  
MBM29LV081@TSOP40 [CX1006] MBM29LV081B@TSOP40 [CX1006]  
MBM29LV116B@TSOP40 [CX1006]  
MBM29LV160B(REVERSE)@TSOP48 [CX1004]  
MBM29LV160B@FBGA48 [CX5022] MBM29LV160B@TSOP48 [CX1004]  
MBM29LV160BE(REVERSE)@TSOP48 [CX1004]  
MBM29LV160BE@FBGA48 [CX5002] MBM29LV160BE@PSOP44 [CX1014]  
MBM29LV160BE@TSOP48 [CX1004] MBM29LV160BM@FBGA48 [CX5002]  
MBM29LV160BM@TSOP48 [CX1004]  
MBM29LV160T(REVERSE)@TSOP48 [CX1004]

MBM29LV160T@FBGA48 [CX5022] MBM29LV160T@TSOP48 [CX1004]  
MBM29LV160TE (REVERSE)@TSOP48 [CX1004]  
MBM29LV160TE@FBGA48 [CX5002] MBM29LV160TE@PSOP44 [CX1014]  
MBM29LV160TE@TSOP48 [CX1004] MBM29LV160TM@FBGA48 [CX5002]  
MBM29LV160TM@TSOP48 [CX1004] MBM29LV200B@PSOP44 [CX1014]  
MBM29LV200B@TSOP48 [CX1004] MBM29LV200BB@PSOP44 [CX1014]  
MBM29LV200BB@TSOP48 [CX1004]  
MBM29LV200BC (REVERSE)@TSOP48 [CX1004]  
MBM29LV200BC@PSOP44 [CX1014] MBM29LV200BC@TSOP48 [CX1004]  
MBM29LV200BT@PSOP44 [CX1014] MBM29LV200BT@TSOP48 [CX1004]  
MBM29LV200T@PSOP44 [CX1014] MBM29LV200T@TSOP48 [CX1004]  
MBM29LV200TC (REVERSE)@TSOP48 [CX1004]  
MBM29LV200TC@PSOP44 [CX1014] MBM29LV200TC@TSOP48 [CX1004]  
MBM29LV320BE (REVERSE)@TSOP48 [CX1004]  
MBM29LV320BE@FBGA63 [CX5063] MBM29LV320BE@TSOP48 [CX1004]  
MBM29LV320TE (REVERSE)@TSOP48 [CX1004]  
MBM29LV320TE@FBGA63 [CX5063] MBM29LV320TE@TSOP48 [CX1004]  
MBM29LV400B@PSOP44 [CX1014] MBM29LV400B@TSOP48 [CX1004]  
MBM29LV400BB@PSOP44 [CX1014] MBM29LV400BB@TSOP48 [CX1004]  
MBM29LV400BC@FBGA48 [CX5002] MBM29LV400BC@PSOP44 [CX1014]  
MBM29LV400BC@TSOP48 [CX1004] MBM29LV400BT@PSOP44 [CX1014]  
MBM29LV400BT@TSOP48 [CX1004] MBM29LV400T@PSOP44 [CX1014]  
MBM29LV400T@TSOP48 [CX1004] MBM29LV400TC@FBGA48 [CX5002]  
MBM29LV400TC@PSOP44 [CX1014] MBM29LV400TC@TSOP48 [CX1004]  
MBM29LV650UE (REVERSE)@TSOP48 [CX1004]  
MBM29LV650UE@TSOP48 [CX1004]  
MBM29LV651UE (REVERSE)@TSOP48 [CX1004]  
MBM29LV651UE@TSOP48 [CX1004] MBM29LV652UE@FBGA63 [CX5041]  
MBM29LV800B@PSOP44 [CX1014] MBM29LV800B@TSOP48 [CX1004]  
MBM29LV800BA (REVERSE)@TSOP48 [CX1004]  
MBM29LV800BA@FBGA48 [CX5039] MBM29LV800BA@PSOP44 [CX1014]  
MBM29LV800BA@TSOP48 [CX1004] MBM29LV800BB@PSOP44 [CX1014]  
MBM29LV800BB@TSOP48 [CX1004]  
MBM29LV800BE (REVERSE)@TSOP48 [CX1004]  
MBM29LV800BE@FBGA48 [CX5039] MBM29LV800BE@PSOP44 [CX1014]  
MBM29LV800BE@TSOP48 [CX1004] MBM29LV800BT@PSOP44 [CX1014]  
MBM29LV800BT@TSOP48 [CX1004] MBM29LV800T@PSOP44 [CX1014]  
MBM29LV800T@TSOP48 [CX1004]  
MBM29LV800TA (REVERSE)@TSOP48 [CX1004]  
MBM29LV800TA@FBGA48 [CX5039] MBM29LV800TA@PSOP44 [CX1014]  
MBM29LV800TA@TSOP48 [CX1004]  
MBM29LV800TE (REVERSE)@TSOP48 [CX1004]  
MBM29LV800TE@FBGA48 [CX5039] MBM29LV800TE@PSOP44 [CX1014]  
MBM29LV800TE@TSOP48 [CX1004] MBM29PDS323B@FBGA63 [CX5047]  
MBM29PDS323T@FBGA63 [CX5047] MBM29PL12LM@TSOP56 [CX1011]  
MBM29PL160BD@PSOP44 [CX1014] MBM29PL160BD@TSOP48 [CX1004]  
MBM29PL160TD@PSOP44 [CX1014] MBM29PL160TD@TSOP48 [CX1004]  
MBM29PL32BM@FBGA48 [CX5002] MBM29PL32BM@TSOP48 [CX1004]  
MBM29PL32TM@FBGA48 [CX5002] MBM29PL32TM@TSOP48 [CX1004]  
MBM29PL64LM@TSOP48 [CX1004] MBM29PL64LM@TSOP56 [CX1011]  
MBM29PL65LM@TSOP48 [CX1004] MBM29QM12DH@FBGA80 [CX5001]  
MBM29QM12DH@TSOP56 [CX1011]  
MBM29SL160BD (REVERSE)@TSOP48 [CX1004]  
MBM29SL160BD@FBGA48 [CX5022] MBM29SL160BD@TSOP48 [CX1004]  
MBM29SL160TD (REVERSE)@TSOP48 [CX1004]  
MBM29SL160TD@FBGA48 [CX5022] MBM29SL160TD@TSOP48 [CX1004]  
MBM29SL800BD (REVERSE)@TSOP48 [CX1004]  
MBM29SL800BD@FBGA48 [CX5022] MBM29SL800BD@TSOP48 [CX1004]  
MBM29SL800BE@FBGA48 [CX5043]



MBM29SL800TD(REVERSE)@TSOP48 [CX1004]  
MBM29SL800TD@FBGA48 [CX5002] MBM29SL800TD@TSOP48 [CX1004]  
MBM29SL800TE@FBGA48 [CX5043] MSP55LV128(fast)@PSOP44 [CX1014]  
MSP55LV128@PSOP44 [CX1014] MSP55LV128T(\*8)@TSOP56 [CX1011]  
MSP55LV128T(fast)@PSOP44 [CX1014]  
MSP55LV128T@PSOP44 [CX1014] MSP55LV128T@TSOP56 [CX1011]  
MSP55LV160@PSOP44 [CX1014] MSP55LV160A@PSOP44 [CX1014]  
MSP55LV512@SSOP70 [CX1057] MSP55LV650@PSOP44 [CX1014]  
PDL127H53V(AM29PDL127H53)@FBGA80 [CX5053]  
PDL127H63V(AM29PDL127H63)@FBGA80 [CX5053]  
PDL127H68V(AM29PDL127H68)@FBGA80 [CX5053]  
PDL127H88V(AM29PDL127H88)@FBGA80 [CX5053]  
PDL129H53V(AM29PDL129H53)@FBGA80 [CX5053]  
PDL129H63V(AM29PDL129H63)@FBGA80 [CX5053]  
PDL129H68V(AM29PDL129H68)@FBGA80 [CX5053]  
PDL129H88V(AM29PDL129H88)@FBGA80 [CX5053]  
S19GL016ATFA00F0@TSOP48 [CX1004] S19GL032ATFA00F0@TSOP48 [CX1004]  
S19MN02GP30TFP00@TSOP48 [CX1004] S25FL001D@SOIC8 [CX1045]  
S25FL001D@USON8 [CX4005] S25FL002A@SOIC8 [CX1044#1]  
S25FL002A@USON8 [CX4005#1] S25FL002D@SOIC8 [CX1045#1]  
S25FL002D@USON8 [CX4005#1] S25FL004A@SOIC8 [CX1044#1]  
S25FL004A@USON8 [CX4005#1] S25FL004D@SOIC8 [CX1045#1]  
S25FL004D@USON8 [CX4005#1]  
S25FL004K@SOIC8(150 mil) [CX1045#1]  
S25FL004K@SOIC8(208 mil) [CX1044#1]  
S25FL008A@SOIC8 [CX1044#1] S25FL008A@USON8 [CX4005#1]  
S25FL008D@SOIC8 [CX1045#1] S25FL008D@USON8 [CX4005#1]  
S25FL008K@SOIC8(150 mil) [CX1045#1]  
S25FL008K@SOIC8(208 mil) [CX1044#1]  
S25FL016A@SOIC16 [CX1033#1] S25FL016A@SOIC16(ISP) [CX0001]  
S25FL016A@SOIC16(Normal mode) [CX1033#1]  
S25FL016A@SOIC8 [CX1044#1] S25FL016A@SOIC8(ISP) [CX0001]  
S25FL016A@SOIC8(Normal mode) [CX1044#1]  
S25FL016A@WSON8 [CX4006#1] S25FL016A@WSON8(ISP) [CX0001]  
S25FL016A@WSON8(Normal mode) [CX4006#1]  
S25FL016K@SOIC16 [CX1033#1]  
S25FL016K@SOIC8(150 mil) [CX1045#1]  
S25FL016K@SOIC8(208 mil) [CX1044#1]  
S25FL020A@SOIC8(4.0) [CX1045#1] S25FL020A@SOIC8(5.4) [CX1044#1]  
S25FL020A@USON8 [CX4005#1] S25FL032A@SOIC16 [CX1033#1]  
S25FL032A@SOIC16(ISP) [CX0001]  
S25FL032A@SOIC16(Normal mode) [CX1033#1]  
S25FL032A@WSON8 [CX4006#1] S25FL032A@WSON8(ISP) [CX0001]  
S25FL032A@WSON8(Normal mode) [CX4006#1]  
S25FL032K@SOIC16 [CX1033#1]  
S25FL032K@SOIC8(150 mil) [CX1045#1]  
S25FL032K@SOIC8(208 mil) [CX1044#1]  
S25FL032P@BGA24(5\*5 pin) [CX5157]  
S25FL032P@BGA24(6\*4 pin) [CX5146]  
S25FL032P@SOIC16 [CX1033#1] S25FL032P@SOIC8 [CX1044#1]  
S25FL032P@USON8 [CX4005#1] S25FL032P@WSON8 [CX4006#1]  
S25FL040A(Bottom Boot)@SOP8(4.0) [CX1045#1]  
S25FL040A(Bottom Boot)@SOP8(5.4) [CX1044#1]  
S25FL040A(Bottom Boot)@USON8 [CX4005#1]  
S25FL040A(Top Boot)@SOP8(4.0) [CX1045#1]  
S25FL040A(Top Boot)@SOP8(5.4) [CX1044#1]  
S25FL040A(Top Boot)@USON8 [CX4005#1]  
S25FL040A@SOP8(4.0) [CX1045#1] S25FL040A@SOP8(5.4) [CX1044#1]  
S25FL040A@USON8 [CX4005#1] S25FL064A@SOIC16 [CX1033#1]

S25FL064A@SOIC16(ISP) [CX0001]  
S25FL064A@SOIC16(Normal mode) [CX1033#1]  
S25FL064A@WSON8 [CX4006#1] S25FL064A@WSON8(ISP) [CX0001]  
S25FL064A@WSON8(Normal mode) [CX4006#1]  
S25FL064K@SOIC16 [CX1033#1]  
S25FL064K@SOIC8(150 mil) [CX1045#1]  
S25FL064K@SOIC8(208 mil) [CX1044#1]  
S25FL064P@BGA24(5\*5pin) [CX5157]  
S25FL064P@BGA24(5\*5pin)(4K bit) [CX5157]  
S25FL064P@BGA24(5\*5pin)(4K)(ch) [CX5157]  
S25FL064P@BGA24(5\*5pin)(ch) [CX5157]  
S25FL064P@BGA24(6\*4pin) [CX5146]  
S25FL064P@BGA24(6\*4pin)(4K bit) [CX5146]  
S25FL064P@BGA24(6\*4pin)(4K)(ch) [CX5146]  
S25FL064P@BGA24(6\*4pin)(ch) [CX5146]  
S25FL064P@SOIC16 [CX1033#1]  
S25FL064P@SOIC16(4K bit) [CX1033#1]  
S25FL064P@SOIC16(4K bit)(ch) [CX1033#1]  
S25FL064P@SOIC16(ch) [CX1033#1] S25FL064P@WSON8 [CX4006#1]  
S25FL064P@WSON8(4K bit) [CX4006#1]  
S25FL064P@WSON8(4K bit)(ch) [CX4006#1]  
S25FL064P@WSON8(ch) [CX4006#1] S25FL080A@SOIC8(4.0) [CX1045#1]  
S25FL080A@SOIC8(5.4) [CX1044#1] S25FL080A@USON8 [CX4005#1]  
S25FL116K@BGA24(4\*6) [CX5146] S25FL116K@BGA24(5\*5) [CX5157]  
S25FL116K@SOIC8(4.0) [CX1045#1] S25FL116K@SOIC8(5.4) [CX1044#1]  
S25FL116K@USON8 [CX4005#1] S25FL127SABBxxx0 [CX5157]  
S25FL127SABBxxx0 [CX5146] S25FL127SABMxxx10 [CX1044#1]  
S25FL127SABNxxx10 [CX4005#1] S25FL128K@SOIC16 [CX1033#1]  
S25FL128P(256 KB)@SOIC16 [CX1033#1]  
S25FL128P(256 KB)@SOIC16(ISP) [CX0001]  
S25FL128P(256 KB)@WSON8 [CX4006#1]  
S25FL128P(256 KB)@WSON8(ISP) [CX0001]  
S25FL128P(64 KB)@SOIC16 [CX1033#1]  
S25FL128P(64 KB)@SOIC16(ISP) [CX0001]  
S25FL128P(64 KB)@WSON8 [CX4006#1]  
S25FL128P(64 KB)@WSON8(ISP) [CX0001]  
S25FL128S(256byte)@BGA24[4\*6] [CX5146]  
S25FL128S(256byte)@BGA24[5\*5] [CX5157]  
S25FL128S(256byte)@SOIC16 [CX1033#1]  
S25FL128S(256byte)@WSON8 [CX4006#1]  
S25FL128S(512byte)@BGA24[4\*6] [CX5146]  
S25FL128S(512byte)@BGA24[5\*5] [CX5157]  
S25FL128S(512byte)@SOIC16 [CX1033#1]  
S25FL128S(512byte)@WSON8 [CX4006#1]  
S25FL128SAGBxxx20 [CX5157] S25FL128SAGBxxx21 [CX5157]  
S25FL128SAGBxxx30 [CX5146] S25FL128SAGBxxx31 [CX5146]  
S25FL128SAGBxxx40 [CX5157] S25FL128SAGBxxx41 [CX5157]  
S25FL128SAGBxxx60 [CX5146] S25FL128SAGBxxx61 [CX5146]  
S25FL128SAGBxxx70 [CX5157] S25FL128SAGBxxx71 [CX5157]  
S25FL128SAGBxxx80 [CX5146] S25FL128SAGBxxx81 [CX5146]  
S25FL128SAGBxxxA0 [CX5157] S25FL128SAGBxxxA1 [CX5157]  
S25FL128SAGBxxxB0 [CX5146] S25FL128SAGBxxxB1 [CX5146]  
S25FL128SAGBxxxC0 [CX5157] S25FL128SAGBxxxC1 [CX5157]  
S25FL128SAGBxxxD0 [CX5146] S25FL128SAGBxxxD1 [CX5146]  
S25FL128SAGBxxxE0 [CX5157] S25FL128SAGBxxxE1 [CX5157]  
S25FL128SAGBxxxF0 [CX5146] S25FL128SAGBxxxF1 [CX5146]  
S25FL128SAGMxxx00 [CX1033#1] S25FL128SAGMxxx01 [CX1033#1]  
S25FL128SAGMxxx90 [CX1033#1] S25FL128SAGMxxx91 [CX1033#1]  
S25FL128SAGMxxxG0 [CX1033#1] S25FL128SAGMxxxG1 [CX1033#1]

S25FL128SAGMxxxH0 [CX1033#1] S25FL128SAGMxxxH1 [CX1033#1]  
S25FL128SAGMxxxQ0 [CX1033#1] S25FL128SAGMxxxQ1 [CX1033#1]  
S25FL128SAGMxxxR0 [CX1033#1] S25FL128SAGMxxxR1 [CX1033#1]  
S25FL128SAGNxxx00 [CX4006#1] S25FL128SAGNxxx01 [CX4006#1]  
S25FL128SAGNxxx90 [CX4006#1] S25FL128SAGNxxx91 [CX4006#1]  
S25FL128SDPBxxx20 [CX5157] S25FL128SDPBxxx21 [CX5157]  
S25FL128SDPBxxx30 [CX5146] S25FL128SDPBxxx31 [CX5146]  
S25FL128SDPBxxx40 [CX5157] S25FL128SDPBxxx41 [CX5157]  
S25FL128SDPBxxx60 [CX5146] S25FL128SDPBxxx61 [CX5146]  
S25FL128SDPBxxx70 [CX5157] S25FL128SDPBxxx71 [CX5157]  
S25FL128SDPBxxx80 [CX5146] S25FL128SDPBxxx81 [CX5146]  
S25FL128SDPBxxxA0 [CX5157] S25FL128SDPBxxxA1 [CX5157]  
S25FL128SDPBxxxB0 [CX5146] S25FL128SDPBxxxB1 [CX5146]  
S25FL128SDPBxxxC0 [CX5157] S25FL128SDPBxxxC1 [CX5157]  
S25FL128SDPBxxxD0 [CX5146] S25FL128SDPBxxxD1 [CX5146]  
S25FL128SDPBxxxE0 [CX5157] S25FL128SDPBxxxE1 [CX5157]  
S25FL128SDPBxxxF0 [CX5146] S25FL128SDPBxxxF1 [CX5146]  
S25FL128SDPMxxx00 [CX1033#1] S25FL128SDPMxxx01 [CX1033#1]  
S25FL128SDPMxxx90 [CX1033#1] S25FL128SDPMxxx91 [CX1033#1]  
S25FL128SDPMxxxG0 [CX1033#1] S25FL128SDPMxxxG1 [CX1033#1]  
S25FL128SDPMxxxH0 [CX1033#1] S25FL128SDPMxxxH1 [CX1033#1]  
S25FL128SDPMxxxQ0 [CX1033#1] S25FL128SDPMxxxQ1 [CX1033#1]  
S25FL128SDPMxxxR0 [CX1033#1] S25FL128SDPMxxxR1 [CX1033#1]  
S25FL128SDPNxxx00 [CX4006#1] S25FL128SDPNxxx01 [CX4006#1]  
S25FL128SDPNxxx90 [CX4006#1] S25FL128SDPNxxx91 [CX4006#1]  
S25FL128SxxxBxxK0 [CX5157] S25FL128SxxxBxxK1 [CX5157]  
S25FL128SxxxBxxL0 [CX5146] S25FL128SxxxBxxL1 [CX5146]  
S25FL128SxxxBxxM0 [CX5157] S25FL128SxxxBxxM1 [CX5157]  
S25FL128SxxxBxxN0 [CX5146] S25FL128SxxxBxxN1 [CX5146]  
S25FL128SxxxBxxS0 [CX5157] S25FL128SxxxBxxS1 [CX5157]  
S25FL128SxxxBxxT0 [CX5146] S25FL128SxxxBxxT1 [CX5146]  
S25FL128SxxxBxxU0 [CX5157] S25FL128SxxxBxxU1 [CX5157]  
S25FL128SxxxBxxV0 [CX5146] S25FL128SxxxBxxV1 [CX5146]  
S25FL128SxxxBxxW0 [CX5157] S25FL128SxxxBxxW1 [CX5157]  
S25FL128SxxxBxxX0 [CX5146] S25FL128SxxxBxxX1 [CX5146]  
S25FL128SxxxBxxY0 [CX5157] S25FL128SxxxBxxY1 [CX5157]  
S25FL128SxxxBxxZ0 [CX5146] S25FL128SxxxBxxZ1 [CX5146]  
S25FL129P@BGA24(5\*5 pin) [CX5157]  
S25FL129P@BGA24(6\*4 pin) [CX5146]  
S25FL129P@SOIC16 [CX1033#1] S25FL129P@WSON8 [CX4006#1]  
S25FL204K@SOIC8[150 mil] [CX1045#1]  
S25FL204K@SOIC8[208 mil] [CX1044#1]  
S25FL208K@SOIC8[150 mil] [CX1045#1]  
S25FL208K@SOIC8[208 mil] [CX1044#1]  
S25FL216K@SOIC8[150 mil] [CX1045#1]  
S25FL216K@SOIC8[208 mil] [CX1044#1]  
S25FL256S(256byte)@BGA24[4\*6] [CX5146]  
S25FL256S(256byte)@BGA24[5\*5] [CX5157]  
S25FL256S(256byte)@SOIC16 [CX1033#1]  
S25FL256S(256byte)@WSON8 [CX4006#1]  
S25FL256S(512byte)@BGA24[4\*6] [CX5146]  
S25FL256S(512byte)@BGA24[5\*5] [CX5157]  
S25FL256S(512byte)@SOIC16 [CX1033#1]  
S25FL256S(512byte)@WSON8 [CX4006#1]  
S25FL256SAGBxxx20 [CX5157] S25FL256SAGBxxx21 [CX5157]  
S25FL256SAGBxxx30 [CX5146] S25FL256SAGBxxx31 [CX5146]  
S25FL256SAGBxxx40 [CX5157] S25FL256SAGBxxx41 [CX5157]  
S25FL256SAGBxxx60 [CX5146] S25FL256SAGBxxx61 [CX5146]  
S25FL256SAGBxxx70 [CX5157] S25FL256SAGBxxx71 [CX5157]

S25FL256SAGBxxx80 [CX5146]	S25FL256SAGBxxx81 [CX5146]
S25FL256SAGBxxxA0 [CX5157]	S25FL256SAGBxxxA1 [CX5157]
S25FL256SAGBxxxB0 [CX5146]	S25FL256SAGBxxxB1 [CX5146]
S25FL256SAGBxxxC0 [CX5157]	S25FL256SAGBxxxC1 [CX5157]
S25FL256SAGBxxxD0 [CX5146]	S25FL256SAGBxxxD1 [CX5146]
S25FL256SAGBxxxE0 [CX5157]	S25FL256SAGBxxxE1 [CX5157]
S25FL256SAGBxxxF0 [CX5146]	S25FL256SAGBxxxF1 [CX5146]
S25FL256SAGMxxx00 [CX1033#1]	S25FL256SAGMxxx01 [CX1033#1]
S25FL256SAGMxxx90 [CX1033#1]	S25FL256SAGMxxx91 [CX1033#1]
S25FL256SAGMxxxG0 [CX1033#1]	S25FL256SAGMxxxG1 [CX1033#1]
S25FL256SAGMxxxH0 [CX1033#1]	S25FL256SAGMxxxH1 [CX1033#1]
S25FL256SAGMxxxQ0 [CX1033#1]	S25FL256SAGMxxxQ1 [CX1033#1]
S25FL256SAGMxxxR0 [CX1033#1]	S25FL256SAGMxxxR1 [CX1033#1]
S25FL256SAGNxxx00 [CX4006#1]	S25FL256SAGNxxx01 [CX4006#1]
S25FL256SAGNxxx90 [CX4006#1]	S25FL256SAGNxxx91 [CX4006#1]
S25FL256SDPBxxx20 [CX5157]	S25FL256SDPBxxx21 [CX5157]
S25FL256SDPBxxx30 [CX5146]	S25FL256SDPBxxx31 [CX5146]
S25FL256SDPBxxx40 [CX5157]	S25FL256SDPBxxx41 [CX5157]
S25FL256SDPBxxx60 [CX5146]	S25FL256SDPBxxx61 [CX5146]
S25FL256SDPBxxx70 [CX5157]	S25FL256SDPBxxx71 [CX5157]
S25FL256SDPBxxx80 [CX5146]	S25FL256SDPBxxx81 [CX5146]
S25FL256SDPBxxxA0 [CX5157]	S25FL256SDPBxxxA1 [CX5157]
S25FL256SDPBxxxB0 [CX5146]	S25FL256SDPBxxxB1 [CX5146]
S25FL256SDPBxxxC0 [CX5157]	S25FL256SDPBxxxC1 [CX5157]
S25FL256SDPBxxxD0 [CX5146]	S25FL256SDPBxxxD1 [CX5146]
S25FL256SDPBxxxE0 [CX5157]	S25FL256SDPBxxxE1 [CX5157]
S25FL256SDPBxxxF0 [CX5146]	S25FL256SDPBxxxF1 [CX5146]
S25FL256SDPMxxx00 [CX1033#1]	S25FL256SDPMxxx01 [CX1033#1]
S25FL256SDPMxxx90 [CX1033#1]	S25FL256SDPMxxx91 [CX1033#1]
S25FL256SDPMxxxG0 [CX1033#1]	S25FL256SDPMxxxG1 [CX1033#1]
S25FL256SDPMxxxH0 [CX1033#1]	S25FL256SDPMxxxH1 [CX1033#1]
S25FL256SDPMxxxQ0 [CX1033#1]	S25FL256SDPMxxxQ1 [CX1033#1]
S25FL256SDPMxxxR0 [CX1033#1]	S25FL256SDPMxxxR1 [CX1033#1]
S25FL256SDPNxxx00 [CX4006#1]	S25FL256SDPNxxx01 [CX4006#1]
S25FL256SDPNxxx90 [CX4006#1]	S25FL256SDPNxxx91 [CX4006#1]
S25FL256SxxxBxK0 [CX5157]	S25FL256SxxxBxK1 [CX5157]
S25FL256SxxxBxL0 [CX5146]	S25FL256SxxxBxL1 [CX5146]
S25FL256SxxxBxM0 [CX5157]	S25FL256SxxxBxM1 [CX5157]
S25FL256SxxxBxN0 [CX5146]	S25FL256SxxxBxN1 [CX5146]
S25FL256SxxxBxS0 [CX5157]	S25FL256SxxxBxS1 [CX5157]
S25FL256SxxxBxT0 [CX5146]	S25FL256SxxxBxT1 [CX5146]
S25FL256SxxxBxU0 [CX5157]	S25FL256SxxxBxU1 [CX5157]
S25FL256SxxxBxV0 [CX5146]	S25FL256SxxxBxV1 [CX5146]
S25FL256SxxxBxW0 [CX5157]	S25FL256SxxxBxW1 [CX5157]
S25FL256SxxxBxX0 [CX5146]	S25FL256SxxxBxX1 [CX5146]
S25FL256SxxxBxY0 [CX5157]	S25FL256SxxxBxY1 [CX5157]
S25FL256SxxxBxZ0 [CX5146]	S25FL256SxxxBxZ1 [CX5146]
S25FL512SAGBxxx20 [CX5157]	S25FL512SAGBxxx30 [CX5146]
S25FL512SAGBxxx40 [CX5157]	S25FL512SAGBxxx60 [CX5146]
S25FL512SAGBxxx70 [CX5157]	S25FL512SAGBxxx80 [CX5146]
S25FL512SAGBxxxA0 [CX5157]	S25FL512SAGBxxxB0 [CX5146]
S25FL512SAGBxxxC0 [CX5157]	S25FL512SAGBxxxD0 [CX5146]
S25FL512SAGBxxxE0 [CX5157]	S25FL512SAGBxxxF0 [CX5146]
S25FL512SAGBxxxK1 [CX5157]	S25FL512SAGBxxxL1 [CX5157]
S25FL512SAGBxxxM1 [CX5157]	S25FL512SAGBxxxN1 [CX5157]
S25FL512SAGBxxxS1 [CX5157]	S25FL512SAGBxxxT1 [CX5157]
S25FL512SAGBxxxU1 [CX5157]	S25FL512SAGBxxxV1 [CX5157]
S25FL512SAGBxxxW1 [CX5157]	S25FL512SAGBxxxX1 [CX5157]
S25FL512SAGBxxxY1 [CX5157]	S25FL512SAGMxxx00 [CX1033#1]

S25FL512SAGMxx90 [CX1033#1]	S25FL512SAGMxxG0 [CX1033#1]
S25FL512SAGMxxH0 [CX1033#1]	S25FL512SAGMxxQ0 [CX1033#1]
S25FL512SAGMxxR0 [CX1033#1]	S25FL512SDPBxx20 [CX5157]
S25FL512SDPBxx30 [CX5146]	S25FL512SDPBxx40 [CX5157]
S25FL512SDPBxx60 [CX5146]	S25FL512SDPBxx70 [CX5157]
S25FL512SDPBxx80 [CX5146]	S25FL512SDPBxxA0 [CX5157]
S25FL512SDPBxxB0 [CX5146]	S25FL512SDPBxxC0 [CX5157]
S25FL512SDPBxxD0 [CX5146]	S25FL512SDPBxxE0 [CX5157]
S25FL512SDPBxxF0 [CX5146]	S25FL512SDPBxxK1 [CX5157]
S25FL512SDPBxxL1 [CX5157]	S25FL512SDPBxxM1 [CX5157]
S25FL512SDPBxxN1 [CX5157]	S25FL512SDPBxxS1 [CX5157]
S25FL512SDPBxxT1 [CX5157]	S25FL512SDPBxxU1 [CX5157]
S25FL512SDPBxxV1 [CX5157]	S25FL512SDPBxxW1 [CX5157]
S25FL512SDPBxxX1 [CX5157]	S25FL512SDPBxxY1 [CX5157]
S25FL512SDPMxx00 [CX1033#1]	S25FL512SDPMxx90 [CX1033#1]
S25FL512SDPMxxG0 [CX1033#1]	S25FL512SDPMxxH0 [CX1033#1]
S25FL512SDPMxxQ0 [CX1033#1]	S25FL512SDPMxxR0 [CX1033#1]
S25FLK05D@SOIC8 [CX1045]	S25FLK05D@USON8 [CX4005]
S25FS256SABNxx01 [CX4006#1]	S25FS256SAGBxx20 [CX5157]
S25FS256SAGBxx30 [CX5146]	S25FS256SAGMxx01 [CX1033#1]
S29AD016D11BFA01@FBGA48 [CX5043]	S29AD016D11BFA02@FBGA48 [CX5043]
S29AD016D11BFB01@FBGA48 [CX5043]	S29AD016D11BFB02@FBGA48 [CX5043]
S29AD016D11BFI01@FBGA48 [CX5043]	S29AD016D11BFI02@FBGA48 [CX5043]
S29AD016D11BFV01@FBGA48 [CX5043]	S29AD016D11BFV02@FBGA48 [CX5043]
S29AD016D11MFA01@PSOP44 [CX1014]	S29AD016D11MFA02@PSOP44 [CX1014]
S29AD016D11MFB01@PSOP44 [CX1014]	S29AD016D11MFB02@PSOP44 [CX1014]
S29AD016D11MFI01@PSOP44 [CX1014]	S29AD016D11MFI02@PSOP44 [CX1014]
S29AD016D11MFV01@PSOP44 [CX1014]	S29AD016D11MFV02@PSOP44 [CX1014]
S29AD016D11TFA01@TSOP48 [CX1004]	S29AD016D11TFA02@TSOP48 [CX1004]
S29AD016D11TFB01@TSOP48 [CX1004]	S29AD016D11TFB02@TSOP48 [CX1004]
S29AD016D11TFI01@TSOP48 [CX1004]	S29AD016D11TFI02@TSOP48 [CX1004]
S29AD016D11TFV01@TSOP48 [CX1004]	S29AD016D11TFV02@TSOP48 [CX1004]
S29AL002B55BAI01@FBGA48 [CX5043]	S29AL002B55BAI02@FBGA48 [CX5043]
S29AL002B55BFI01@FBGA48 [CX5043]	S29AL002B55BFI02@FBGA48 [CX5043]
S29AL002B55MAI01@PSOP44 [CX1014]	S29AL002B55MAI02@PSOP44 [CX1014]
S29AL002B55MFI01@PSOP44 [CX1014]	S29AL002B55MFI02@PSOP44 [CX1014]
S29AL002B55TAI01@TSOP48 [CX1004]	S29AL002B55TAI02@TSOP48 [CX1004]
S29AL002B55TFI01@TSOP48 [CX1004]	S29AL002B55TFI02@TSOP48 [CX1004]
S29AL004B55BAI01@FBGA48 [CX5043]	S29AL004B55BAI02@FBGA48 [CX5043]
S29AL004B55BFI01@FBGA48 [CX5043]	S29AL004B55BFI02@FBGA48 [CX5043]
S29AL004B55MAI01@PSOP44 [CX1014]	S29AL004B55MAI02@PSOP44 [CX1014]
S29AL004B55MFI01@PSOP44 [CX1014]	S29AL004B55MFI02@PSOP44 [CX1014]
S29AL004B55TAI01@TSOP48 [CX1004]	S29AL004B55TAI02@TSOP48 [CX1004]
S29AL004B55TFI01@TSOP48 [CX1004]	S29AL004B55TFI02@TSOP48 [CX1004]
S29AL004D55BAI01@FBGA48 [CX5043]	S29AL004D55BAI02@FBGA48 [CX5043]
S29AL004D55BANR1@FBGA48 [CX5043]	S29AL004D55BANR2@FBGA48 [CX5043]
S29AL004D55BFI01@FBGA48 [CX5043]	S29AL004D55BFI02@FBGA48 [CX5043]
S29AL004D55BFNR1@FBGA48 [CX5043]	S29AL004D55BFNR2@FBGA48 [CX5043]
S29AL004D55MAI01@PSOP44 [CX1014]	S29AL004D55MAI02@PSOP44 [CX1014]
S29AL004D55MANR1@PSOP44 [CX1014]	S29AL004D55MANR2@PSOP44 [CX1014]
S29AL004D55MFI01@PSOP44 [CX1014]	S29AL004D55MFI02@PSOP44 [CX1014]
S29AL004D55MFNR1@PSOP44 [CX1014]	S29AL004D55MFNR2@PSOP44 [CX1014]
S29AL004D55TAI01@TSOP48 [CX1004]	S29AL004D55TAI02@TSOP48 [CX1004]
S29AL004D55TANR1@TSOP48 [CX1004]	S29AL004D55TANR2@TSOP48 [CX1004]
S29AL004D55TFI01@TSOP48 [CX1004]	S29AL004D55TFI02@TSOP48 [CX1004]
S29AL004D55TFNR1@TSOP48 [CX1004]	S29AL004D55TFNR2@TSOP48 [CX1004]
S29AL004D70BAI01@FBGA48 [CX5043]	S29AL004D70BAI02@FBGA48 [CX5043]
S29AL004D70BAN01@FBGA48 [CX5043]	S29AL004D70BAN02@FBGA48 [CX5043]
S29AL004D70BFI01@FBGA48 [CX5043]	S29AL004D70BFI02@FBGA48 [CX5043]





S29AL016M10BAIR1@FBGA48 [CX5002] S29AL016M10BAIR2@FBGA48 [CX5002]  
S29AL016M10BFI01@FBGA48 [CX5002] S29AL016M10BFI02@FBGA48 [CX5002]  
S29AL016M10BFIR1@FBGA48 [CX5002] S29AL016M10BFIR2@FBGA48 [CX5002]  
S29AL016M10FAI01@FBGA64 [CX5074] S29AL016M10FAI02@FBGA64 [CX5074]  
S29AL016M10FAIR1@FBGA64 [CX5074] S29AL016M10FAIR2@FBGA64 [CX5074]  
S29AL016M10FFI01@FBGA64 [CX5074] S29AL016M10FFI02@FBGA64 [CX5074]  
S29AL016M10FFIR1@FBGA64 [CX5074] S29AL016M10FFIR2@FBGA64 [CX5074]  
S29AL016M10TAI01@TSOP48 [CX1004] S29AL016M10TAI02@TSOP48 [CX1004]  
S29AL016M10TAIR1@TSOP48 [CX1004] S29AL016M10TAIR2@TSOP48 [CX1004]  
S29AL016M10TFI01@TSOP48 [CX1004] S29AL016M10TFI02@TSOP48 [CX1004]  
S29AL016M10TFIR1@TSOP48 [CX1004] S29AL016M10TFIR2@TSOP48 [CX1004]  
S29AL016M90BAI01@FBGA48 [CX5002] S29AL016M90BAI02@FBGA48 [CX5002]  
S29AL016M90BAIR1@FBGA48 [CX5002] S29AL016M90BAIR2@FBGA48 [CX5002]  
S29AL016M90BFI01@FBGA48 [CX5002] S29AL016M90BFI02@FBGA48 [CX5002]  
S29AL016M90BFIR1@FBGA48 [CX5002] S29AL016M90BFIR2@FBGA48 [CX5002]  
S29AL016M90FAI01@FBGA64 [CX5074] S29AL016M90FAI02@FBGA64 [CX5074]  
S29AL016M90FAIR1@FBGA64 [CX5074] S29AL016M90FAIR2@FBGA64 [CX5074]  
S29AL016M90FFI01@FBGA64 [CX5074] S29AL016M90FFI02@FBGA64 [CX5074]  
S29AL016M90FFIR1@FBGA64 [CX5074] S29AL016M90FFIR2@FBGA64 [CX5074]  
S29AL016M90TAI01@TSOP48 [CX1004] S29AL016M90TAI02@TSOP48 [CX1004]  
S29AL016M90TAIR1@TSOP48 [CX1004] S29AL016M90TAIR2@TSOP48 [CX1004]  
S29AL016M90TFI01@TSOP48 [CX1004] S29AL016M90TFI02@TSOP48 [CX1004]  
S29AL016M90TFIR1@TSOP48 [CX1004] S29AL016M90TFIR2@TSOP48 [CX1004]  
S29AL032D70BAI00@FBGA48 [CX5083] S29AL032D70BAI03@FBGA48 [CX5083]  
S29AL032D70BAI04@FBGA48 [CX5083] S29AL032D70BFI00@FBGA48 [CX5083]  
S29AL032D70BFI03(new)@FBGA48 [CX5083]  
S29AL032D70BFI03@FBGA48 [CX5083]  
S29AL032D70BFI04(new)@FBGA48 [CX5083]  
S29AL032D70BFI04@FBGA48 [CX5083] S29AL032D70TAI00@TSOP40 [CX1006]  
S29AL032D70TAI03@TSOP48 [CX1004] S29AL032D70TAI04@TSOP48 [CX1004]  
S29AL032D70TFI00@TSOP40 [CX1006] S29AL032D70TFI03@TSOP48 [CX1004]  
S29AL032D70TFI04@TSOP48 [CX1004] S29AL032D90BAI00@FBGA48 [CX5083]  
S29AL032D90BAI03@FBGA48 [CX5083] S29AL032D90BAI04@FBGA48 [CX5083]  
S29AL032D90BAN00@FBGA48 [CX5083] S29AL032D90BAN03@FBGA48 [CX5083]  
S29AL032D90BAN04@FBGA48 [CX5083] S29AL032D90BFI00@FBGA48 [CX5083]  
S29AL032D90BFI03@FBGA48 [CX5083] S29AL032D90BFI04@FBGA48 [CX5083]  
S29AL032D90BFN00@FBGA48 [CX5083] S29AL032D90BFN03@FBGA48 [CX5083]  
S29AL032D90BFN04@FBGA48 [CX5083] S29AL032D90TAI00@TSOP40 [CX1006]  
S29AL032D90TAI03@TSOP48 [CX1004] S29AL032D90TAI04@TSOP48 [CX1004]  
S29AL032D90TAN00@TSOP40 [CX1006] S29AL032D90TAN03@TSOP48 [CX1004]  
S29AL032D90TAN04@TSOP48 [CX1004] S29AL032D90TFI00@TSOP40 [CX1006]  
S29AL032D90TFI03@TSOP48 [CX1004]  
S29AL032D90TFI03@TSOP48(SLOW) [CX1004]  
S29AL032D90TFI04@TSOP48 [CX1004] S29AL032D90TFN00@TSOP40 [CX1006]  
S29AL032D90TFN03@TSOP48 [CX1004] S29AL032D90TFN04@TSOP48 [CX1004]  
S29AS008J70BFI01@FBGA48 [CX5043] S29AS008J70BFI02@FBGA48 [CX5043]  
S29AS008J70BFI03@FBGA48 [CX5043] S29AS008J70BFI04@FBGA48 [CX5043]  
S29AS008J70TFI01@TSOP48 [CX1004] S29AS008J70TFI02@TSOP48 [CX1004]  
S29AS008J70TFI03@TSOP48 [CX1004] S29AS008J70TFI04@TSOP48 [CX1004]  
S29AS016J70BFI01@FBGA48 [CX5043] S29AS016J70BFI02@FBGA48 [CX5043]  
S29AS016J70BFI03@FBGA48 [CX5043] S29AS016J70BFI04@FBGA48 [CX5043]  
S29AS016J70BHIF3@WFBGA48 [CX5037]  
S29AS016J70BHIF4@WFBGA48 [CX5037]  
S29AS016J70TFI01@TSOP48 [CX1004] S29AS016J70TFI02@TSOP48 [CX1004]  
S29AS016J70TFI03@TSOP48 [CX1004] S29AS016J70TFI04@TSOP48 [CX1004]  
S29GL016A10BAI01@FBGA48 [CX5043] S29GL016A10BAI02@FBGA48 [CX5043]  
S29GL016A10BAI03@FBGA48 [CX5043] S29GL016A10BAI04@FBGA48 [CX5043]  
S29GL016A10BAIR1@FBGA48 [CX5043] S29GL016A10BAIR2@FBGA48 [CX5043]  
S29GL016A10BAIR3@FBGA48 [CX5043] S29GL016A10BAIR4@FBGA48 [CX5043]





S29GL01GP12FAIS1@FBGA64 [CX5074]	S29GL01GP12FAIS2@FBGA64 [CX5074]
S29GL01GP12FAIV1@FBGA64 [CX5074]	S29GL01GP12FAIV2@FBGA64 [CX5074]
S29GL01GP12FFI01@FBGA64 [CX5074]	S29GL01GP12FFI02@FBGA64 [CX5074]
S29GL01GP12FFIS1@FBGA64 [CX5074]	S29GL01GP12FFIS2@FBGA64 [CX5074]
S29GL01GP12FFIV1@FBGA64 [CX5074]	S29GL01GP12FFIV2@FBGA64 [CX5074]
S29GL01GP12TAI01@TSOP56 [CX1011]	S29GL01GP12TAI02@TSOP56 [CX1011]
S29GL01GP12TAIV1@TSOP56 [CX1011]	S29GL01GP12TAIV2@TSOP56 [CX1011]
S29GL01GP12TFI01@TSOP56 [CX1011]	S29GL01GP12TFI02@TSOP56 [CX1011]
S29GL01GP12TFIV1@TSOP56 [CX1011]	S29GL01GP12TFIV2@TSOP56 [CX1011]
S29GL01GP13FAI01@FBGA64 [CX5074]	S29GL01GP13FAI02@FBGA64 [CX5074]
S29GL01GP13FAIS5@FBGA64 [CX5074]	S29GL01GP13FAIS6@FBGA64 [CX5074]
S29GL01GP13FAIV1@FBGA64 [CX5074]	S29GL01GP13FAIV2@FBGA64 [CX5074]
S29GL01GP13FFI01@FBGA64 [CX5074]	S29GL01GP13FFI02@FBGA64 [CX5074]
S29GL01GP13FFIS5@FBGA64 [CX5074]	S29GL01GP13FFIS6@FBGA64 [CX5074]
S29GL01GP13FFIV1@FBGA64 [CX5074]	S29GL01GP13FFIV2@FBGA64 [CX5074]
S29GL01GP13TAI01@TSOP56 [CX1011]	S29GL01GP13TAI02@TSOP56 [CX1011]
S29GL01GP13TAIV1@TSOP56 [CX1011]	S29GL01GP13TAIV2@TSOP56 [CX1011]
S29GL01GP13TFI01@TSOP56 [CX1011]	S29GL01GP13TFI02@TSOP56 [CX1011]
S29GL01GP13TFIV1@TSOP56 [CX1011]	S29GL01GP13TFIV2@TSOP56 [CX1011]
S29GL01GP90FAI01@FBGA64 [CX5074]	S29GL01GP90FAI02@FBGA64 [CX5074]
S29GL01GP90FFI01@FBGA64 [CX5074]	S29GL01GP90FFI02@FBGA64 [CX5074]
S29GL01GP90TAI01@TSOP56 [CX1011]	S29GL01GP90TAI02@TSOP56 [CX1011]
S29GL01GP90TFI01@TSOP56 [CX1011]	S29GL01GP90TFI02@TSOP56 [CX1011]
S29GL01GR11FFCR1@FBGA64 [CX5103]	S29GL01GR11FFCR2@FBGA64 [CX5103]
S29GL01GR11FFCS7@FBGA64 [CX5103]	S29GL01GR11FFCS8@FBGA64 [CX5103]
S29GL01GR11FFIR1@FBGA64 [CX5103]	S29GL01GR11FFIR2@FBGA64 [CX5103]
S29GL01GR11TFCR1@TSOP56 [CX1011]	S29GL01GR11TFCR2@TSOP56 [CX1011]
S29GL01GR11TFIR1@TSOP56 [CX1011]	S29GL01GR11TFIR2@TSOP56 [CX1011]
S29GL01GR12DFI01@FBGA64 [CX5074]	S29GL01GR12DFI02@FBGA64 [CX5074]
S29GL01GR12TFI01@TSOP56 [CX1011]	S29GL01GR12TFI02@TSOP56 [CX1011]
S29GL01GR13DFIV1@FBGA64 [CX5074]	S29GL01GR13DFIV2@FBGA64 [CX5074]
S29GL01GR13TFIV1@TSOP56 [CX1011]	S29GL01GR13TFIV2@TSOP56 [CX1011]
S29GL01GS10DHI01@FBGA64 [CX5103]	S29GL01GS10DHI02@FBGA64 [CX5103]
S29GL01GS10DHSS1@FBGA64 [CX5103]	S29GL01GS10DHSS2@FBGA64 [CX5103]
S29GL01GS10DHSS3 [CX5103]	S29GL01GS10DHSS4 [CX5103]
S29GL01GS10DHSS5 [CX5103]	S29GL01GS10DHSS6 [CX5103]
S29GL01GS10DHSS7 [CX5103]	S29GL01GS10DHSS8 [CX5103]
S29GL01GS10FHI01@FBGA64 [CX5074]	S29GL01GS10FHI02@FBGA64 [CX5074]
S29GL01GS10FHSS1@FBGA64 [CX5074]	S29GL01GS10FHSS2@FBGA64 [CX5074]
S29GL01GS10FHSS3 [CX5074]	S29GL01GS10FHSS4 [CX5074]
S29GL01GS10FHSS5 [CX5074]	S29GL01GS10FHSS6 [CX5074]
S29GL01GS10FHSS7 [CX5074]	S29GL01GS10FHSS8 [CX5074]
S29GL01GS10TFI01@TSOP56 [CX1011]	S29GL01GS10TFI02@TSOP56 [CX1011]
S29GL01GS11DHI01@FBGA64 [CX5103]	S29GL01GS11DHI02@FBGA64 [CX5103]
S29GL01GS11DHIV1@FBGA64 [CX5103]	S29GL01GS11DHIV2@FBGA64 [CX5103]
S29GL01GS11DHSS1@FBGA64 [CX5103]	S29GL01GS11DHSS2@FBGA64 [CX5103]
S29GL01GS11DHSS3 [CX5103]	S29GL01GS11DHSS4 [CX5103]
S29GL01GS11DHSS5 [CX5103]	S29GL01GS11DHSS6 [CX5103]
S29GL01GS11DHSS7 [CX5103]	S29GL01GS11DHSS8 [CX5103]
S29GL01GS11FHI01@FBGA64 [CX5074]	S29GL01GS11FHI02@FBGA64 [CX5074]
S29GL01GS11FHIV1@FBGA64 [CX5074]	S29GL01GS11FHIV2@FBGA64 [CX5074]
S29GL01GS11FHSS1@FBGA64 [CX5074]	S29GL01GS11FHSS2@FBGA64 [CX5074]
S29GL01GS11FHSS3 [CX5074]	S29GL01GS11FHSS4 [CX5074]
S29GL01GS11FHSS5 [CX5074]	S29GL01GS11FHSS6 [CX5074]
S29GL01GS11FHSS7 [CX5074]	S29GL01GS11FHSS8 [CX5074]
S29GL01GS11TFI01@TSOP56 [CX1011]	S29GL01GS11TFI02@TSOP56 [CX1011]
S29GL01GS11TFIV1@TSOP56 [CX1011]	S29GL01GS11TFIV2@TSOP56 [CX1011]
S29GL01GS12DHIV1@FBGA64 [CX5103]	S29GL01GS12DHIV2@FBGA64 [CX5103]
S29GL01GS12FHIV1@FBGA64 [CX5074]	S29GL01GS12FHIV2@FBGA64 [CX5074]











S29GL064N11FAIS1@FBGA64 [CX5074] S29GL064N11FAIS2@FBGA64 [CX5074]  
S29GL064N11FAIS3 (HD)@FBGA64 [CX5004]  
S29GL064N11FAIS3@FBGA64 [CX5004] S29GL064N11FAIS4@FBGA64 [CX5004]  
S29GL064N11FAIV1@FBGA64 [CX5074] S29GL064N11FAIV2@FBGA64 [CX5074]  
S29GL064N11FFIS1@FBGA64 [CX5074] S29GL064N11FFIS2@FBGA64 [CX5074]  
S29GL064N11FFIS3 (HD)@FBGA64 [CX5004]  
S29GL064N11FFIS3@FBGA64 [CX5004] S29GL064N11FFIS4@FBGA64 [CX5004]  
S29GL064N11FFIV1@FBGA64 [CX5074] S29GL064N11FFIV2@FBGA64 [CX5074]  
S29GL064N11TAIV1@TSOP56 [CX1011] S29GL064N11TAIV2@TSOP56 [CX1011]  
S29GL064N11TAIV6@TSOP48 [CX1004] S29GL064N11TAIV7@TSOP48 [CX1004]  
S29GL064N11TFIV1@TSOP56 [CX1011] S29GL064N11TFIV2@TSOP56 [CX1011]  
S29GL064N11TFIV6@TSOP48 [CX1004] S29GL064N11TFIV7@TSOP48 [CX1004]  
S29GL064N70BAI03@FBGA48 [CX5043] S29GL064N70BAI04@FBGA48 [CX5043]  
S29GL064N70BAIR3@FBGA48 [CX5043] S29GL064N70BAIR4@FBGA48 [CX5043]  
S29GL064N70BFI03@FBGA48 [CX5043] S29GL064N70BFI04@FBGA48 [CX5043]  
S29GL064N70BFIR3@FBGA48 [CX5043] S29GL064N70BFIR4@FBGA48 [CX5043]  
S29GL064N70FAI01@FBGA64 [CX5074] S29GL064N70FAI02@FBGA64 [CX5074]  
S29GL064N70FAI03@FBGA64 [CX5074] S29GL064N70FAI04@FBGA64 [CX5074]  
S29GL064N70FAIR1@FBGA64 [CX5074] S29GL064N70FAIR2@FBGA64 [CX5074]  
S29GL064N70FAIR3@FBGA64 [CX5074] S29GL064N70FAIR4@FBGA64 [CX5074]  
S29GL064N70FFI01@FBGA64 [CX5074] S29GL064N70FFI02@FBGA64 [CX5074]  
S29GL064N70FFI03@FBGA64 [CX5074] S29GL064N70FFI04@FBGA64 [CX5074]  
S29GL064N70FFIR1@FBGA64 [CX5074] S29GL064N70FFIR2@FBGA64 [CX5074]  
S29GL064N70FFIR3@FBGA64 [CX5074] S29GL064N70FFIR4@FBGA64 [CX5074]  
S29GL064N70TAI01@TSOP56 [CX1011] S29GL064N70TAI02@TSOP56 [CX1011]  
S29GL064N70TAI03@TSOP48 [CX1004] S29GL064N70TAI04@TSOP48 [CX1004]  
S29GL064N70TAI06@TSOP48 [CX1004] S29GL064N70TAI07@TSOP48 [CX1004]  
S29GL064N70TAIR2@TSOP56 [CX1011] S29GL064N70TAIR3@TSOP48 [CX1004]  
S29GL064N70TAIR4@TSOP48 [CX1004] S29GL064N70TAIR6@TSOP48 [CX1004]  
S29GL064N70TAIR7@TSOP48 [CX1004] S29GL064N70TFI01@TSOP56 [CX1011]  
S29GL064N70TFI02@TSOP56 [CX1011] S29GL064N70TFI03@TSOP48 [CX1004]  
S29GL064N70TFI04@TSOP48 [CX1004] S29GL064N70TFI06@TSOP48 [CX1004]  
S29GL064N70TFI07@TSOP48 [CX1004] S29GL064N70TFIR1@TSOP56 [CX1011]  
S29GL064N70TFIR2@TSOP56 [CX1011] S29GL064N70TFIR3@TSOP48 [CX1004]  
S29GL064N70TFIR4@TSOP48 [CX1004] S29GL064N70TFIR6@TSOP48 [CX1004]  
S29GL064N70TFIR7@TSOP48 [CX1004] S29GL064N90BAI03@FBGA48 [CX5043]  
S29GL064N90BAI04@FBGA48 [CX5043] S29GL064N90BAIR3@FBGA48 [CX5043]  
S29GL064N90BAIR4@FBGA48 [CX5043] S29GL064N90BFI03@FBGA48 [CX5043]  
S29GL064N90BFI04@FBGA48 [CX5043] S29GL064N90BFIR3@FBGA48 [CX5043]  
S29GL064N90BFIR4@FBGA48 [CX5043] S29GL064N90DAI01@FBGA64 [CX5103]  
S29GL064N90DAI02@FBGA64 [CX5103] S29GL064N90DAI03@FBGA64 [CX5103]  
S29GL064N90DAI04@FBGA64 [CX5103] S29GL064N90DFI01@FBGA64 [CX5103]  
S29GL064N90DFI02@FBGA64 [CX5103] S29GL064N90DFI03@FBGA64 [CX5103]  
S29GL064N90DFI04@FBGA64 [CX5103] S29GL064N90FAI01@FBGA64 [CX5074]  
S29GL064N90FAI02@FBGA64 [CX5074] S29GL064N90FAI03@FBGA64 [CX5074]  
S29GL064N90FAI04@FBGA64 [CX5074] S29GL064N90FAIR1@FBGA64 [CX5074]  
S29GL064N90FAIR2@FBGA64 [CX5074] S29GL064N90FAIR3@FBGA64 [CX5074]  
S29GL064N90FAIR4@FBGA64 [CX5074] S29GL064N90FAIS1@FBGA64 [CX5074]  
S29GL064N90FAIS2@FBGA64 [CX5074]  
S29GL064N90FAIS3 (HD)@FBGA64 [CX5004]  
S29GL064N90FAIS3@FBGA64 [CX5004] S29GL064N90FAIS4@FBGA64 [CX5004]  
S29GL064N90FAIV1@FBGA64 [CX5074] S29GL064N90FAIV2@FBGA64 [CX5074]  
S29GL064N90FFI01@FBGA64 [CX5074] S29GL064N90FFI02@FBGA64 [CX5074]  
S29GL064N90FFI03@FBGA64 [CX5074] S29GL064N90FFI04@FBGA64 [CX5074]  
S29GL064N90FFIR1@FBGA64 [CX5074] S29GL064N90FFIR2@FBGA64 [CX5074]  
S29GL064N90FFIR3@FBGA64 [CX5074] S29GL064N90FFIR4@FBGA64 [CX5074]  
S29GL064N90FFIS1@FBGA64 [CX5074] S29GL064N90FFIS2@FBGA64 [CX5074]  
S29GL064N90FFIS3 (HD)@FBGA64 [CX5004]  
S29GL064N90FFIS3@FBGA64 [CX5004] S29GL064N90FFIS4@FBGA64 [CX5004]





S29GL128N11TFIV1@TSOP56 [CX1011]	S29GL128N11TFIV2@TSOP56 [CX1011]
S29GL128N11TIW01@TSOP56 [CX1011]	S29GL128N11TIW02@TSOP56 [CX1011]
S29GL128N90FAIR1@FBGA64 [CX5074]	S29GL128N90FAIR2@FBGA64 [CX5074]
S29GL128N90FFIR1@FBGA64 [CX5074]	S29GL128N90FFIR2@FBGA64 [CX5074]
S29GL128N90TAIR1@TSOP56 [CX1011]	S29GL128N90TAIR2@TSOP56 [CX1011]
S29GL128N90TFIR1@TSOP56 [CX1011]	S29GL128N90TFIR2@TSOP56 [CX1011]
S29GL128P10DAIS1@FBGA64 [CX5103]	S29GL128P10DAIS2@FBGA64 [CX5103]
S29GL128P10DFIS1@FBGA64 [CX5103]	S29GL128P10DFIS2@FBGA64 [CX5103]
S29GL128P10FAI01@FBGA64 [CX5074]	S29GL128P10FAI02@FBGA64 [CX5074]
S29GL128P10FAIS1@FBGA64 [CX5074]	S29GL128P10FAIS2@FBGA64 [CX5074]
S29GL128P10FAIS3@FBGA64 [CX5004]	S29GL128P10FAIS4@FBGA64 [CX5004]
S29GL128P10FFI01@FBGA64 [CX5074]	S29GL128P10FFI02@FBGA64 [CX5074]
S29GL128P10FFIS1@FBGA64 [CX5074]	S29GL128P10FFIS2@FBGA64 [CX5074]
S29GL128P10FFIS3@FBGA64 [CX5004]	S29GL128P10FFIS4@FBGA64 [CX5004]
S29GL128P10TAI01@TSOP56 [CX1011]	S29GL128P10TAI02@TSOP56 [CX1011]
S29GL128P10TFI01(FH)@TSOP56 [CX1011]	
S29GL128P10TFI01@TSOP56 [CX1011]	S29GL128P10TFI02@TSOP56 [CX1011]
S29GL128P11DAIS1@FBGA64 [CX5103]	S29GL128P11DAIS2@FBGA64 [CX5103]
S29GL128P11DAIS5@FBGA64 [CX5103]	S29GL128P11DAIS6@FBGA64 [CX5103]
S29GL128P11DFIS1@FBGA64 [CX5103]	S29GL128P11DFIS2@FBGA64 [CX5103]
S29GL128P11DFIS5@FBGA64 [CX5103]	S29GL128P11DFIS6@FBGA64 [CX5103]
S29GL128P11FAI01@FBGA64 [CX5074]	S29GL128P11FAI02@FBGA64 [CX5074]
S29GL128P11FAIS1@FBGA64 [CX5074]	S29GL128P11FAIS2@FBGA64 [CX5074]
S29GL128P11FAIS3@FBGA64 [CX5004]	S29GL128P11FAIS4@FBGA64 [CX5004]
S29GL128P11FAIS5@FBGA64 [CX5074]	S29GL128P11FAIS6@FBGA64 [CX5074]
S29GL128P11FAIV1@FBGA64 [CX5074]	S29GL128P11FAIV2@FBGA64 [CX5074]
S29GL128P11FFI01@FBGA64 [CX5074]	S29GL128P11FFI02@FBGA64 [CX5074]
S29GL128P11FFIS1@FBGA64 [CX5074]	S29GL128P11FFIS2@FBGA64 [CX5074]
S29GL128P11FFIS3@FBGA64 [CX5004]	S29GL128P11FFIS4@FBGA64 [CX5004]
S29GL128P11FFIS5@FBGA64 [CX5074]	S29GL128P11FFIS6@FBGA64 [CX5074]
S29GL128P11FFIV1@FBGA64 [CX5074]	S29GL128P11FFIV2@FBGA64 [CX5074]
S29GL128P11TAI01@TSOP56 [CX1011]	S29GL128P11TAI02@TSOP56 [CX1011]
S29GL128P11TAIV1@TSOP56 [CX1011]	S29GL128P11TAIV2@TSOP56 [CX1011]
S29GL128P11TFI01@TSOP56 [CX1011]	S29GL128P11TFI02@TSOP56 [CX1011]
S29GL128P11TFIV1@TSOP56 [CX1011]	S29GL128P11TFIV2@TSOP56 [CX1011]
S29GL128P90DAIS7@FBGA64 [CX5103]	S29GL128P90DAIS8@FBGA64 [CX5103]
S29GL128P90DFIS7@FBGA64 [CX5103]	S29GL128P90DFIS8@FBGA64 [CX5103]
S29GL128P90FACR1@FBGA64 [CX5074]	S29GL128P90FACR2@FBGA64 [CX5074]
S29GL128P90FAIR1@FBGA64 [CX5074]	S29GL128P90FAIR2@FBGA64 [CX5074]
S29GL128P90FAIS0@FBGA64 [CX5004]	S29GL128P90FAIS7@FBGA64 [CX5074]
S29GL128P90FAIS8@FBGA64 [CX5074]	S29GL128P90FAIS9@FBGA64 [CX5004]
S29GL128P90FASS0@FBGA64 [CX5004]	S29GL128P90FASS7@FBGA64 [CX5074]
S29GL128P90FASS8@FBGA64 [CX5074]	S29GL128P90FASS9@FBGA64 [CX5004]
S29GL128P90FFCR1@FBGA64 [CX5074]	S29GL128P90FFCR2@FBGA64 [CX5074]
S29GL128P90FFIR1@FBGA64 [CX5074]	S29GL128P90FFIR2@FBGA64 [CX5074]
S29GL128P90FFIS0@FBGA64 [CX5004]	S29GL128P90FFIS7@FBGA64 [CX5074]
S29GL128P90FFIS8@FBGA64 [CX5074]	S29GL128P90FFIS9@FBGA64 [CX5004]
S29GL128P90FFSS0@FBGA64 [CX5004]	S29GL128P90FFSS7@FBGA64 [CX5074]
S29GL128P90FFSS8@FBGA64 [CX5074]	S29GL128P90FFSS9@FBGA64 [CX5004]
S29GL128P90TACR1@TSOP56 [CX1011]	S29GL128P90TACR2@TSOP56 [CX1011]
S29GL128P90TAIR1@TSOP56 [CX1011]	S29GL128P90TAIR2@TSOP56 [CX1011]
S29GL128P90TFCR1@TSOP56 [CX1011]	S29GL128P90TFCR2@TSOP56 [CX1011]
S29GL128P90TFIR1@TSOP56 [CX1011]	S29GL128P90TFIR2@TSOP56 [CX1011]
S29GL128S@SSOP56 [CX0051]	S29GL128S10DHI01@FBGA64 [CX5103]
S29GL128S10DHI02@FBGA64 [CX5103]	S29GL128S10DHIV1@FBGA64 [CX5103]
S29GL128S10DHIV2@FBGA64 [CX5103]	S29GL128S10DHSS1@FBGA64 [CX5103]
S29GL128S10DHSS2@FBGA64 [CX5103]	S29GL128S10DHSS3@FBGA64 [CX5103]
S29GL128S10DHSS4@FBGA64 [CX5103]	S29GL128S10DHSS5@FBGA64 [CX5103]
S29GL128S10DHSS6@FBGA64 [CX5103]	S29GL128S10DHSS7@FBGA64 [CX5103]

S29GL128S10DHSS8@FBGA64 [CX5103] S29GL128S10FHI01@FBGA64 [CX5074]  
S29GL128S10FHI02@FBGA64 [CX5074] S29GL128S10FHIV1@FBGA64 [CX5074]  
S29GL128S10FHIV2@FBGA64 [CX5074] S29GL128S10FHSS1@FBGA64 [CX5074]  
S29GL128S10FHSS2@FBGA64 [CX5074] S29GL128S10FHSS3@FBGA64 [CX5074]  
S29GL128S10FHSS4@FBGA64 [CX5074] S29GL128S10FHSS5@FBGA64 [CX5074]  
S29GL128S10FHSS6@FBGA64 [CX5074] S29GL128S10FHSS7@FBGA64 [CX5074]  
S29GL128S10FHSS8@FBGA64 [CX5074] S29GL128S10TFI01@TSOP56 [CX1011]  
S29GL128S10TFI02@TSOP56 [CX1011] S29GL128S10TFIV1@TSOP56 [CX1011]  
S29GL128S10TFIV2@TSOP56 [CX1011] S29GL128S11DHIV1@FBGA64 [CX5103]  
S29GL128S11DHIV2@FBGA64 [CX5103] S29GL128S11FHIV1@FBGA64 [CX5074]  
S29GL128S11FHIV2@FBGA64 [CX5074] S29GL128S11TFIV1@TSOP56 [CX1011]  
S29GL128S11TFIV2@TSOP56 [CX1011] S29GL128S90DHI01@FBGA64 [CX5103]  
S29GL128S90DHI02@FBGA64 [CX5103] S29GL128S90DHSS1@FBGA64 [CX5103]  
S29GL128S90DHSS2@FBGA64 [CX5103] S29GL128S90DHSS3@FBGA64 [CX5103]  
S29GL128S90DHSS4@FBGA64 [CX5103] S29GL128S90DHSS5@FBGA64 [CX5103]  
S29GL128S90DHSS6@FBGA64 [CX5103] S29GL128S90DHSS7@FBGA64 [CX5103]  
S29GL128S90DHSS8@FBGA64 [CX5103] S29GL128S90FHI01@FBGA64 [CX5074]  
S29GL128S90FHI02@FBGA64 [CX5074] S29GL128S90FHSS1@FBGA64 [CX5074]  
S29GL128S90FHSS2@FBGA64 [CX5074] S29GL128S90FHSS3@FBGA64 [CX5074]  
S29GL128S90FHSS4@FBGA64 [CX5074] S29GL128S90FHSS5@FBGA64 [CX5074]  
S29GL128S90FHSS6@FBGA64 [CX5074] S29GL128S90FHSS7@FBGA64 [CX5074]  
S29GL128S90FHSS8@FBGA64 [CX5074] S29GL128S90GHI01@FBGA56 [CX5045]  
S29GL128S90GHI02@FBGA56 [CX5045] S29GL128S90TFI01@TSOP56 [CX1011]  
S29GL128S90TFI02@TSOP56 [CX1011] S29GL200GS@FBGA54 [CX5004]  
S29GL202GP@FBGA54 [CX5004] S29GL256M10FAIR1@FBGA64 [CX5075]  
S29GL256M10FAIR2@FBGA64 [CX5075] S29GL256M10FFIR1@FBGA64 [CX5075]  
S29GL256M10FFIR2@FBGA64 [CX5075] S29GL256M10TAIR1@TSOP56 [CX1011]  
S29GL256M10TAIR2@TSOP56 [CX1011] S29GL256M10TFIR1@TSOP56 [CX1011]  
S29GL256M10TFIR2@TSOP56 [CX1011] S29GL256M11FAIR1@FBGA64 [CX5075]  
S29GL256M11FAIR2@FBGA64 [CX5075] S29GL256M11FFIR1@FBGA64 [CX5075]  
S29GL256M11FFIR2@FBGA64 [CX5075] S29GL256M11TAIR1@TSOP56 [CX1011]  
S29GL256M11TAIR2@TSOP56 [CX1011] S29GL256M11TFIR1@TSOP56 [CX1011]  
S29GL256M11TFIR2@TSOP56 [CX1011] S29GL256M15TDWN2@TSOP56 [CX1011]  
S29GL256N10FAI01@FBGA64 [CX5074] S29GL256N10FAI02@FBGA64 [CX5074]  
S29GL256N10FAIS1@FBGA64 [CX5074] S29GL256N10FAIS2@FBGA64 [CX5074]  
S29GL256N10FAIS3@FBGA64 [CX5004] S29GL256N10FAIS4@FBGA64 [CX5004]  
S29GL256N10FFI01@FBGA64 [CX5074] S29GL256N10FFI02@FBGA64 [CX5074]  
S29GL256N10FFIS1@FBGA64 [CX5074] S29GL256N10FFIS2@FBGA64 [CX5074]  
S29GL256N10FFIS3@FBGA64 [CX5004] S29GL256N10FFIS4@FBGA64 [CX5004]  
S29GL256N10TAI01@TSOP56 [CX1011] S29GL256N10TAI02@TSOP56 [CX1011]  
S29GL256N10TFI01@TSOP56 [CX1011] S29GL256N10TFI02@TSOP56 [CX1011]  
S29GL256N11FAI01@FBGA64 [CX5074] S29GL256N11FAI02@FBGA64 [CX5074]  
S29GL256N11FAI1H@FBGA64 [CX5004] S29GL256N11FAIS1@FBGA64 [CX5074]  
S29GL256N11FAIS2@FBGA64 [CX5074] S29GL256N11FAIS3@FBGA64 [CX5004]  
S29GL256N11FAIS4@FBGA64 [CX5004] S29GL256N11FAIV1@FBGA64 [CX5074]  
S29GL256N11FAIV2@FBGA64 [CX5074] S29GL256N11FFI01@FBGA64 [CX5074]  
S29GL256N11FFI02@FBGA64 [CX5074] S29GL256N11FFI1H@FBGA64 [CX5004]  
S29GL256N11FFIS1@FBGA64 [CX5074] S29GL256N11FFIS2@FBGA64 [CX5074]  
S29GL256N11FFIS3@FBGA64 [CX5004] S29GL256N11FFIS4@FBGA64 [CX5004]  
S29GL256N11FFIV1@FBGA64 [CX5074] S29GL256N11FFIV2@FBGA64 [CX5074]  
S29GL256N11TAI01@TSOP56 [CX1011] S29GL256N11TAI02@TSOP56 [CX1011]  
S29GL256N11TAIV1@TSOP56 [CX1011] S29GL256N11TAIV2@TSOP56 [CX1011]  
S29GL256N11TFI01@TSOP56 [CX1011] S29GL256N11TFI02@TSOP56 [CX1011]  
S29GL256N11TFIV1@TSOP56 [CX1011] S29GL256N11TFIV2@TSOP56 [CX1011]  
S29GL256N90FAIR1@FBGA64 [CX5074] S29GL256N90FAIR2@FBGA64 [CX5074]  
S29GL256N90FFIR1@FBGA64 [CX5074] S29GL256N90FFIR2@FBGA64 [CX5074]  
S29GL256N90TAIR1@TSOP56 [CX1011] S29GL256N90TAIR2@TSOP56 [CX1011]  
S29GL256N90TFIR1@TSOP56 [CX1011] S29GL256N90TFIR2@TSOP56 [CX1011]  
S29GL256NT(low)@TSOP56 [CX1011] S29GL256P10DAIS1@FBGA64 [CX5103]



S29GL256S10TFIV2@TSOP56 [CX1011]	S29GL256S11DHIV1@FBGA64 [CX5103]
S29GL256S11DHIV2@FBGA64 [CX5103]	S29GL256S11FHIV1@FBGA64 [CX5074]
S29GL256S11FHIV2@FBGA64 [CX5074]	S29GL256S11TFIV1@TSOP56 [CX1011]
S29GL256S11TFIV2@TSOP56 [CX1011]	S29GL256S90DHI01@FBGA64 [CX5103]
S29GL256S90DHI02@FBGA64 [CX5103]	S29GL256S90DHSS1@FBGA64 [CX5103]
S29GL256S90DHSS2@FBGA64 [CX5103]	S29GL256S90DHSS3@FBGA64 [CX5103]
S29GL256S90DHSS4@FBGA64 [CX5103]	S29GL256S90DHSS5@FBGA64 [CX5103]
S29GL256S90DHSS6@FBGA64 [CX5103]	S29GL256S90DHSS7@FBGA64 [CX5103]
S29GL256S90DHSS8@FBGA64 [CX5103]	S29GL256S90FHI01@FBGA64 [CX5074]
S29GL256S90FHI02@FBGA64 [CX5074]	S29GL256S90FHSS1@FBGA64 [CX5074]
S29GL256S90FHSS2@FBGA64 [CX5074]	S29GL256S90FHSS3@FBGA64 [CX5074]
S29GL256S90FHSS4@FBGA64 [CX5074]	S29GL256S90FHSS5@FBGA64 [CX5074]
S29GL256S90FHSS6@FBGA64 [CX5074]	S29GL256S90FHSS7@FBGA64 [CX5074]
S29GL256S90FHSS8@FBGA64 [CX5074]	S29GL256S90GHI01@FBGA56 [CX5045]
S29GL256S90GHI02@FBGA56 [CX5045]	S29GL256S90TFI01@TSOP56 [CX1011]
S29GL256S90TFI02@TSOP56 [CX1011]	S29GL512N10FAI01@FBGA64 [CX5074]
S29GL512N10FAI02@FBGA64 [CX5074]	S29GL512N10FAIS1@FBGA64 [CX5074]
S29GL512N10FAIS2@FBGA64 [CX5074]	S29GL512N10FFI01@FBGA64 [CX5074]
S29GL512N10FFI02@FBGA64 [CX5074]	S29GL512N10FFIS1@FBGA64 [CX5074]
S29GL512N10FFIS2@FBGA64 [CX5074]	S29GL512N10TAI01@TSOP56 [CX1011]
S29GL512N10TAI02@TSOP56 [CX1011]	S29GL512N10TFI01@TSOP56 [CX1011]
S29GL512N10TFI02@TSOP56 [CX1011]	S29GL512N11FAI01@FBGA64 [CX5074]
S29GL512N11FAI02@FBGA64 [CX5074]	S29GL512N11FAIS1@FBGA64 [CX5074]
S29GL512N11FAIS2@FBGA64 [CX5074]	S29GL512N11FAIV1@FBGA64 [CX5074]
S29GL512N11FAIV2@FBGA64 [CX5074]	S29GL512N11FFI01@FBGA64 [CX5074]
S29GL512N11FFI02@FBGA64 [CX5074]	S29GL512N11FFIS1@FBGA64 [CX5074]
S29GL512N11FFIS2@FBGA64 [CX5074]	S29GL512N11FFIV1@FBGA64 [CX5074]
S29GL512N11FFIV2@FBGA64 [CX5074]	S29GL512N11TAI01@TSOP56 [CX1011]
S29GL512N11TAI02@TSOP56 [CX1011]	S29GL512N11TAIV1@TSOP56 [CX1011]
S29GL512N11TAIV2@TSOP56 [CX1011]	S29GL512N11TFI01@TSOP56 [CX1011]
S29GL512N11TFI02@TSOP56 [CX1011]	S29GL512N11TFIV1@TSOP56 [CX1011]
S29GL512N11TFIV2@TSOP56 [CX1011]	S29GL512P10DAIS1@FBGA64 [CX5103]
S29GL512P10DAIS2@FBGA64 [CX5103]	S29GL512P10DAIS7@FBGA64 [CX5103]
S29GL512P10DAIS8@FBGA64 [CX5103]	S29GL512P10DFIS1@FBGA64 [CX5103]
S29GL512P10DFIS2@FBGA64 [CX5103]	S29GL512P10DFIS7@FBGA64 [CX5103]
S29GL512P10DFIS8@FBGA64 [CX5103]	S29GL512P10FACR1@FBGA64 [CX5074]
S29GL512P10FACR2@FBGA64 [CX5074]	S29GL512P10FAI01@FBGA64 [CX5074]
S29GL512P10FAI02@FBGA64 [CX5074]	S29GL512P10FAIR1@FBGA64 [CX5074]
S29GL512P10FAIR2@FBGA64 [CX5074]	S29GL512P10FAIS1@FBGA64 [CX5074]
S29GL512P10FAIS2@FBGA64 [CX5074]	S29GL512P10FAIS7@FBGA64 [CX5074]
S29GL512P10FAIS8@FBGA64 [CX5074]	S29GL512P10FASS7@FBGA64 [CX5074]
S29GL512P10FASS8@FBGA64 [CX5074]	S29GL512P10FFCR1@FBGA64 [CX5074]
S29GL512P10FFCR2@FBGA64 [CX5074]	S29GL512P10FFI01@FBGA64 [CX5074]
S29GL512P10FFI02@FBGA64 [CX5074]	S29GL512P10FFIR1@FBGA64 [CX5074]
S29GL512P10FFIR2@FBGA64 [CX5074]	S29GL512P10FFIS1@FBGA64 [CX5074]
S29GL512P10FFIS2@FBGA64 [CX5074]	S29GL512P10FFIS7@FBGA64 [CX5074]
S29GL512P10FFIS8@FBGA64 [CX5074]	S29GL512P10FFSS7@FBGA64 [CX5074]
S29GL512P10FFSS8@FBGA64 [CX5074]	S29GL512P10TACR1@TSOP56 [CX1011]
S29GL512P10TACR2@TSOP56 [CX1011]	S29GL512P10TAI01@TSOP56 [CX1011]
S29GL512P10TAI02@TSOP56 [CX1011]	S29GL512P10TAIR1@TSOP56 [CX1011]
S29GL512P10TAIR2@TSOP56 [CX1011]	S29GL512P10TFCR1@TSOP56 [CX1011]
S29GL512P10TFCR2@TSOP56 [CX1011]	S29GL512P10TFI01@TSOP56 [CX1011]
S29GL512P10TFI02@TSOP56 [CX1011]	S29GL512P10TFIR1@TSOP56 [CX1011]
S29GL512P10TFIR2@TSOP56 [CX1011]	S29GL512P11DAIS1@FBGA64 [CX5103]
S29GL512P11DAIS2@FBGA64 [CX5103]	S29GL512P11DAIS5@FBGA64 [CX5103]
S29GL512P11DAIS6@FBGA64 [CX5103]	S29GL512P11DFIS1@FBGA64 [CX5103]
S29GL512P11DFIS2@FBGA64 [CX5103]	S29GL512P11DFIS5@FBGA64 [CX5103]
S29GL512P11DFIS6@FBGA64 [CX5103]	S29GL512P11FAI01@FBGA64 [CX5074]
S29GL512P11FAI02@FBGA64 [CX5074]	S29GL512P11FAIS1@FBGA64 [CX5074]

S29GL512P11FAIS2@FBGA64 [CX5074]	S29GL512P11FAIS5@FBGA64 [CX5074]
S29GL512P11FAIS6@FBGA64 [CX5074]	S29GL512P11FAIV1@FBGA64 [CX5074]
S29GL512P11FAIV2@FBGA64 [CX5074]	S29GL512P11FFI01@FBGA64 [CX5074]
S29GL512P11FFI02@FBGA64 [CX5074]	S29GL512P11FFIS1@FBGA64 [CX5074]
S29GL512P11FFIS2@FBGA64 [CX5074]	S29GL512P11FFIS5@FBGA64 [CX5074]
S29GL512P11FFIS6@FBGA64 [CX5074]	S29GL512P11FFIV1@FBGA64 [CX5074]
S29GL512P11FFIV2@FBGA64 [CX5074]	S29GL512P11TAI01@TSOP56 [CX1011]
S29GL512P11TAI02@TSOP56 [CX1011]	S29GL512P11TAIV1@TSOP56 [CX1011]
S29GL512P11TAIV2@TSOP56 [CX1011]	S29GL512P11TFI01@TSOP56 [CX1011]
S29GL512P11TFI02@TSOP56 [CX1011]	S29GL512P11TFIV1@TSOP56 [CX1011]
S29GL512P11TFIV2@TSOP56 [CX1011]	S29GL512P12DAIS5@FABG64 [CX5103]
S29GL512P12DAIS6@FABG64 [CX5103]	S29GL512P12DFIS5@FABG64 [CX5103]
S29GL512P12DFIS6@FABG64 [CX5103]	S29GL512P12FAIS5@FBGA64 [CX5074]
S29GL512P12FAIS6@FBGA64 [CX5074]	S29GL512P12FAIV1@FBGA64 [CX5074]
S29GL512P12FAIV2@FBGA64 [CX5074]	S29GL512P12FFIS5@FBGA64 [CX5074]
S29GL512P12FFIS6@FBGA64 [CX5074]	S29GL512P12FFIV1@FBGA64 [CX5074]
S29GL512P12FFIV2@FBGA64 [CX5074]	S29GL512P12TAIV1@TSOP56 [CX1011]
S29GL512P12TAIV2@TSOP56 [CX1011]	S29GL512P12TFIV1@TSOP56 [CX1011]
S29GL512P12TFIV2@TSOP56 [CX1011]	S29GL512R10FFCR1@FBGA64 [CX5103]
S29GL512R10FFCR2@FBGA64 [CX5103]	S29GL512R10FFCS7@FBGA64 [CX5103]
S29GL512R10FFCS8@FBGA64 [CX5103]	S29GL512R10FFIR1@FBGA64 [CX5103]
S29GL512R10FFIR2@FBGA64 [CX5103]	S29GL512R10TFCR1@TSOP56 [CX1011]
S29GL512R10TFCR2@TSOP56 [CX1011]	S29GL512R10TFIR1@TSOP56 [CX1011]
S29GL512R10TFIR2@TSOP56 [CX1011]	S29GL512R11DFI01@FBGA64 [CX5074]
S29GL512R11DFI02@FBGA64 [CX5074]	S29GL512R11TFI01@TSOP56 [CX1011]
S29GL512R11TFI02@TSOP56 [CX1011]	S29GL512R12DFIV1@FBGA64 [CX5074]
S29GL512R12DFIV2@FBGA64 [CX5074]	S29GL512R12TFIV1@TSOP56 [CX1011]
S29GL512R12TFIV2@TSOP56 [CX1011]	S29GL512S10DHI01@FBGA64 [CX5103]
S29GL512S10DHI02@FBGA64 [CX5103]	S29GL512S10DHIV1@FBGA64 [CX5103]
S29GL512S10DHIV2@FBGA64 [CX5103]	S29GL512S10DHSS1@FBGA64 [CX5103]
S29GL512S10DHSS2@FBGA64 [CX5103]	S29GL512S10DHSS3@FBGA64 [CX5103]
S29GL512S10DHSS4@FBGA64 [CX5103]	S29GL512S10DHSS5@FBGA64 [CX5103]
S29GL512S10DHSS6@FBGA64 [CX5103]	S29GL512S10DHSS7@FBGA64 [CX5103]
S29GL512S10DHSS8@FBGA64 [CX5103]	S29GL512S10FHI01@FBGA64 [CX5074]
S29GL512S10FHI02@FBGA64 [CX5074]	S29GL512S10FHSS1@FBGA64 [CX5074]
S29GL512S10FHSS2@FBGA64 [CX5074]	S29GL512S10FHSS3@FBGA64 [CX5074]
S29GL512S10FHSS4@FBGA64 [CX5074]	S29GL512S10FHSS5@FBGA64 [CX5074]
S29GL512S10FHSS6@FBGA64 [CX5074]	S29GL512S10FHSS7@FBGA64 [CX5074]
S29GL512S10FHSS8@FBGA64 [CX5074]	S29GL512S10GHI01@FBGA56 [CX5045]
S29GL512S10GHI02@FBGA56 [CX5045]	S29GL512S10TFI01@TSOP56 [CX1011]
S29GL512S10TFI02@TSOP56 [CX1011]	S29GL512S11DHI01@FBGA64 [CX5103]
S29GL512S11DHI02@FBGA64 [CX5103]	S29GL512S11DHIV1@FBGA64 [CX5103]
S29GL512S11DHIV2@FBGA64 [CX5103]	S29GL512S11DHSS1@FBGA64 [CX5103]
S29GL512S11DHSS2@FBGA64 [CX5103]	S29GL512S11DHSS3@FBGA64 [CX5103]
S29GL512S11DHSS4@FBGA64 [CX5103]	S29GL512S11DHSS5@FBGA64 [CX5103]
S29GL512S11DHSS6@FBGA64 [CX5103]	S29GL512S11DHSS7@FBGA64 [CX5103]
S29GL512S11DHSS8@FBGA64 [CX5103]	S29GL512S11FHI01@FBGA64 [CX5074]
S29GL512S11FHI02@FBGA64 [CX5074]	S29GL512S11FHIV1@FBGA64 [CX5074]
S29GL512S11FHIV2@FBGA64 [CX5074]	S29GL512S11FHSS1@FBGA64 [CX5074]
S29GL512S11FHSS2@FBGA64 [CX5074]	S29GL512S11FHSS3@FBGA64 [CX5074]
S29GL512S11FHSS4@FBGA64 [CX5074]	S29GL512S11FHSS5@FBGA64 [CX5074]
S29GL512S11FHSS6@FBGA64 [CX5074]	S29GL512S11FHSS7@FBGA64 [CX5074]
S29GL512S11FHSS8@FBGA64 [CX5074]	S29GL512S11TFI01@TSOP56 [CX1011]
S29GL512S11TFI02@TSOP56 [CX1011]	S29GL512S11TFIV1@TSOP56 [CX1011]
S29GL512S11TFIV2@TSOP56 [CX1011]	S29GL512S12DHIV1@FBGA64 [CX5103]
S29GL512S12DHIV2@FBGA64 [CX5103]	S29GL512S12FHIV1@FBGA64 [CX5074]
S29GL512S12FHIV2@FBGA64 [CX5074]	S29GL512S12TFIV1@TSOP56 [CX1011]
S29GL512S12TFIV2@TSOP56 [CX1011]	S29JL032H55BAI01@FBGA48 [CX5043]
S29JL032H55BAI02@FBGA48 [CX5043]	S29JL032H55BAI21@FBGA48 [CX5043]



S29JL032H90TFI02@TSOP48 [CX1004]	S29JL032H90TFI21@TSOP48 [CX1004]
S29JL032H90TFI22@TSOP48 [CX1004]	S29JL032H90TFI31@TSOP48 [CX1004]
S29JL032H90TFI32@TSOP48 [CX1004]	S29JL032H90TFI41@TSOP48 [CX1004]
S29JL032H90TFI42@TSOP48 [CX1004]	S29JL032J60BHI31@FBGA48 [CX5043]
S29JL032J60BHI32@FBGA48 [CX5043]	S29JL032J60TFI01@TSOP48 [CX1004]
S29JL032J60TFI02@TSOP48 [CX1004]	S29JL032J60TFI21@TSOP48 [CX1004]
S29JL032J60TFI22@TSOP48 [CX1004]	S29JL032J60TFI31@TSOP48 [CX1004]
S29JL032J60TFI32@TSOP48 [CX1004]	S29JL032J60TFI41@TSOP48 [CX1004]
S29JL032J60TFI42@TSOP48 [CX1004]	S29JL032J70BHI31@FBGA48 [CX5043]
S29JL032J70BHI32@FBGA48 [CX5043]	S29JL032J70TFI01@TSOP48 [CX1004]
S29JL032J70TFI02@TSOP48 [CX1004]	S29JL032J70TFI21@TSOP48 [CX1004]
S29JL032J70TFI22@TSOP48 [CX1004]	S29JL032J70TFI31@TSOP48 [CX1004]
S29JL032J70TFI32@TSOP48 [CX1004]	S29JL032J70TFI41@TSOP48 [CX1004]
S29JL032J70TFI42@TSOP48 [CX1004]	S29JL064H55BAI00@FBGA63 [CX5041]
S29JL064H55BFI00@FBGA63 [CX5041]	S29JL064H55TAI00@TSOP48 [CX1004]
S29JL064H55TFI00@TSOP48 [CX1004]	S29JL064H60BAI00@FBGA63 [CX5041]
S29JL064H60BFI00@FBGA63 [CX5041]	S29JL064H60TAI00@TSOP48 [CX1004]
S29JL064H60TFI00@TSOP48 [CX1004]	S29JL064H70BAI00@FBGA63 [CX5041]
S29JL064H70BFI00@FBGA63 [CX5041]	S29JL064H70TAI00@TSOP48 [CX1004]
S29JL064H70TAN00@TSOP48 [CX1004]	S29JL064H70TFI00@TSOP48 [CX1004]
S29JL064H70TFN00@TSOP48 [CX1004]	S29JL064H90BAI00@FBGA63 [CX5041]
S29JL064H90BFI00@FBGA63 [CX5041]	S29JL064H90TAI00@TSOP48 [CX1004]
S29JL064H90TAN00@TSOP48 [CX1004]	S29JL064H90TFI00@TSOP48 [CX1004]
S29JL064H90TFN00@TSOP48 [CX1004]	S29JL064J55BHI00@FBGA48 [CX5043]
S29JL064J55TFI00@TSOP48 [CX1004]	S29JL064J60BHI00@FBGA48 [CX5043]
S29JL064J60TFI00@TSOP48 [CX1004]	S29JL064J70BHI00@FBGA48 [CX5043]
S29JL064J70TFI00@TSOP48 [CX1004]	S29NS016J0LBFW00@FBGA44 [CX5094]
S29NS016J0LBJW00@FBGA44 [CX5094]	S29NS016J0PBFW00@FBGA44 [CX5094]
S29NS016J0PB JW00@FBGA44 [CX5094]	S29NS032J0LBFW00@FBGA44 [CX5094]
S29NS032J0LBJW00@FBGA44 [CX5094]	S29NS032J0PBFW00@FBGA44 [CX5094]
S29NS032J0PB JW00@FBGA44 [CX5094]	S29NS064J0LBAW00@FBGA44 [CX5066]
S29NS064J0LBFW00@FBGA44 [CX5066]	S29NS064J0LBJW00@FBGA44 [CX5066]
S29NS064J0PB AW00@FBGA44 [CX5066]	S29NS064J0PBFW00@FBGA44 [CX5066]
S29NS064J0PB JW00@FBGA44 [CX5066]	S29NS064N0PB JW00@FBGA44 [CX5067]
S29NS128J0LBAW00@FBGA48 [CX50UN]	S29NS128J0LBFW00@FBGA48 [CX50UN]
S29NS128J0LBJW00@FBGA48 [CX50UN]	S29NS128J0PB AW00@FBGA48 [CX50UN]
S29NS128J0PBFW00@FBGA48 [CX50UN]	S29NS128J0PB JW00@FBGA48 [CX50UN]
S29NS128N0PB JW00@FBGA44 [CX5066]	S29NS128P0PB JW00@FBGA44 [CX5067]
S29NS128P0SBJW00@FBGA44 [CX5067]	S29NS128PABBJW00@FBGA44 [CX5067]
S29NS128R0PBHW00@FBGA44 [CX5067]	S29NS128R0SBHW00@FBGA44 [CX5067]
S29NS128RAABHW00@FBGA44 [CX5067]	S29NS256N0PB JW00@FBGA48 [CX50UN]
S29NS256P0PB JW00@FBGA44 [CX5067]	S29NS256P0SBJW00@FBGA44 [CX5067]
S29NS256PABBJW00@FBGA44 [CX5067]	S29NS256R0PBHW00@FBGA44 [CX5067]
S29NS256R0SBHW00@FBGA44 [CX5067]	S29NS256RAABHW00@FBGA44 [CX5067]
S29NS512P0PB JW00@FBGA64 [CX5066]	S29NS512P0SBJW00@FBGA64 [CX5066]
S29NS512PABBJW00@FBGA64 [CX5066]	S29PL032J55BAI12@FBGA48 [CX5043]
S29PL032J55BAI15@FBGA56 [CX5045]	S29PL032J55BAW12@FBGA48 [CX5043]
S29PL032J55BAW15@FBGA56 [CX5045]	S29PL032J55BFI12@FBGA48 [CX5043]
S29PL032J55BFI15@FBGA56 [CX5045]	S29PL032J55BFW12@FBGA48 [CX5043]
S29PL032J55BFW15@FBGA56 [CX5045]	S29PL032J60BAI12@FBGA48 [CX5043]
S29PL032J60BAI15@FBGA56 [CX5045]	S29PL032J60BAW12@FBGA48 [CX5043]
S29PL032J60BAW15@FBGA56 [CX5045]	S29PL032J60BFI12@FBGA48 [CX5043]
S29PL032J60BFI15@FBGA56 [CX5045]	S29PL032J60BFW12@FBGA48 [CX5043]
S29PL032J60BFW15@FBGA56 [CX5045]	S29PL032J70BAI12@FBGA48 [CX5043]
S29PL032J70BAI15@FBGA56 [CX5045]	S29PL032J70BAW12@FBGA48 [CX5043]
S29PL032J70BAW15@FBGA56 [CX5045]	S29PL032J70BFI12@FBGA48 [CX5043]
S29PL032J70BFI15@FBGA56 [CX5045]	S29PL032J70BFW12@FBGA48 [CX5043]
S29PL032J70BFW15@FBGA56 [CX5045]	S29PL064J55BAI12@FBGA48 [CX5043]
S29PL064J55BAI15@FBGA56 [CX5045]	S29PL064J55BAW12@FBGA48 [CX5043]









S29WS512R0SBFW20@FBGA84 [CX5001]	S29WS512R0SBFW40@FBGA84 [CX5001]
S29WS512R0SBHW00@FBGA84 [CX5001]	S29WS512R0SBHW20@FBGA84 [CX5001]
S29WS512R0SBHW40@FBGA84 [CX5001]	S29WS512RAABFW00@FBGA84 [CX5001]
S29WS512RAABFW20@FBGA84 [CX5001]	S29WS512RAABFW40@FBGA84 [CX5001]
S29WS512RAABHW00@FBGA84 [CX5001]	S29WS512RAABHW20@FBGA84 [CX5001]
S29WS512RAABHW40@FBGA84 [CX5001]	S29WS512RAGBFW00@FBGA84 [CX5001]
S29WS512RAGBFW20@FBGA84 [CX5001]	S29WS512RAGBFW40@FBGA84 [CX5001]
S29WS512RAGBHW00@FBGA84 [CX5001]	S29WS512RAGBHW20@FBGA84 [CX5001]
S29WS512RAGBHW40@FBGA84 [CX5001]	S30ML01GP30TFE00@TSOP48 [CX1004]
S30ML01GP30TFE50@TSOP48 [CX1004]	S30ML01GP50TFE01@TSOP48 [CX1004]
S30ML01GP50TFE51@TSOP48 [CX1004]	S30ML02GP30TFE00@TSOP48 [CX1004]
S30ML02GP30TFE50@TSOP48 [CX1004]	S30ML02GP50TFE01@TSOP48 [CX1004]
S30ML02GP50TFE51@TSOP48 [CX1004]	S30ML128P30TFE00@TSOP48 [CX1004]
S30ML128P30TFE50@TSOP48 [CX1004]	S30ML128P50TFE01@TSOP48 [CX1004]
S30ML128P50TFE51@TSOP48 [CX1004]	S30ML256P30TFE00@TSOP48 [CX1004]
S30ML256P30TFE50@TSOP48 [CX1004]	S30ML256P50TFE01@TSOP48 [CX1004]
S30ML256P50TFE51@TSOP48 [CX1004]	S30ML512P30TFI50@TSOP48 [CX1004]
S30ML512P50TFE01@TSOP48 [CX1004]	S30ML512P50TFE51@TSOP48 [CX1004]
S30MS01GP25TFW01@TSOP48 [CX1004]	S30MS01GP25TFW50@TSOP48 [CX1004]
S30MS01GP25TFW51@TSOP48 [CX1004]	S30MS01GR25TFW10@TSOP48 [CX1004]
S30MS01GR25TFW11@TSOP48 [CX1004]	S30MS02GR25TFW01@TSOP48 [CX1004]
S30MS02GR25TFW10@TSOP48 [CX1004]	S30MS512R25TFW10@TSOP48 [CX1004]
S30MS512R25TFW11@TSOP48 [CX1004]	S34ML01G100BHI00@FBGA63 [CX5046]
S34ML01G100TFI00@TSOP48 [CX1004-1]	
S34ML01G200TFI00@TSOP48 [CX1004-1]	
S34ML02G100BHI00@FBGA63 [CX5046]	
S34ML02G100TFI00@TSOP48 [CX1004-1]	
S34ML04G100BHI00@FBGA63 [CX5046]	
S34ML04G100TFI00@TSOP48 [CX1004-1]	
S34ML04G200TFI00@TSOP48 [CX1004-1]	
S70FL01GSAGMxx01 [CX1033#1]	S70FL01GSDPMxx01 [CX1033#1]
S70FL256P@BGA24 [CX5157]	S70FL256P@SOP16 [CX1033#1]
S70FL512P@BGA24 [CX5157]	S70FL512P@SOP16 [CX1033#1]
S70FL512S@BGA24 [CX5157]	S70FL512S@SOP16 [CX1033#1]
S70GL02GP11FAIR1@FBGA64 [CX5074]	S70GL02GP11FAIR2@FBGA64 [CX5074]
S70GL02GP11FFIR1@FBGA64 [CX5074]	S70GL02GP11FFIR2@FBGA64 [CX5074]
S70GL02GP12FAI01@FBGA64 [CX5074]	S70GL02GP12FAI02@FBGA64 [CX5074]
S70GL02GP12FFI01@FBGA64 [CX5074]	S70GL02GP12FFI02@FBGA64 [CX5074]
S70GL02GP13FAIV1@FBGA64 [CX5074]	S70GL02GP13FAIV2@FBGA64 [CX5074]
S70GL02GP13FFIV1@FBGA64 [CX5074]	S70GL02GP13FFIV2@FBGA64 [CX5074]
S70GL02GS11FHI01@FBGA64 [CX5074]	S70GL02GS11FHI02@FBGA64 [CX5074]
S70GL02GS12FHIV1@FBGA64 [CX5074]	S70GL02GS12FHIV2@FBGA64 [CX5074]
S70PL254J00BAW91@FBGA64 [CX5001]	S70PL254J00BAW93@FBGA64 [CX5001]
S70PL254J00BAWA1@FBGA84 [CX5001]	S70PL254J00BAWA3@FBGA84 [CX5001]
S70PL254J00BFW91@FBGA64 [CX5001]	S70PL254J00BFW93@FBGA64 [CX5001]
S70PL254J00BFWA1@FBGA84 [CX5001]	S70PL254J00BFWA3@FBGA84 [CX5001]
S70PL512N00BAW53@FBGA84 [CX5001]	S70PL512N00BFW53@FBGA84 [CX5001]
S70PL512N00HAW53@FBGA84 [CX5001]	S70PL512N00HFW53@FBGA84 [CX5001]
S71AL016D02BAWB7@FBGA56 [CX5045]	S71AL016D02BAWBF@FBGA56 [CX5045]
S71AL016D02BAWT7@FBGA56 [CX5045]	S71AL016D02BAWTF@FBGA56 [CX5045]
S71AL016D02BFWB7@FBGA56 [CX5045]	S71AL016D02BFWBF@FBGA56 [CX5045]
S71AL016D02BFWT7@FBGA56 [CX5045]	S71AL016D02BFWTF@FBGA56 [CX5045]
S71AL016D04BAWBX@FBGA56 [CX5045]	S71AL016D04BAWTF@FBGA56 [CX5045]
S71AL016D04BFWBX@FBGA56 [CX5045]	S71AL016D04BFWTX@FBGA56 [CX5045]
S71AL016M40BAW0B@FBGA56 [CX5045]	S71AL016M40BAW0F@FBGA56 [CX5045]
S71AL016M40BFW0B@FBGA56 [CX5045]	S71AL016M40BFW0F@FBGA56 [CX5045]
S71GL016A40BAW1J@FBGA56 [CX5045]	S71GL016A40BAW3J@FBGA56 [CX5045]
S71GL016A40BFW1J@FBGA56 [CX5045]	S71GL016A40BFW3J@FBGA56 [CX5045]
S71GL032A08BAW0B@FBGA56 [CX5045]	S71GL032A08BAW0F@FBGA56 [CX5045]







S71NS064JA0BFW21@FBGA44 [CX5066] S71NS064JA0BJWRN@FBGA56 [CX5066]  
S71NS064N80BHWRA@FBGA56 [CX5066] S71NS064N80BJWRA@FBGA56 [CX5066]  
S71NS064NA0BHWRA@FBGA56 [CX5066] S71NS064NA0BHWRN@FBGA56 [CX5066]  
S71NS064NA0BJWRA@FBGA56 [CX5066] S71NS064NA0BJWRN@FBGA56 [CX5066]  
S71NS064NA0BJWRN@FBGA56(ZTE) [CX5183]  
S71NS064NB0BHWUN@FBGA56 [CX5066] S71NS064NB0BJWUN@FBGA56 [CX5066]  
S71NS128JA0BAW01@FBGA48 [CX50UN] S71NS128JA0BAW11@FBGA48 [CX50UN]  
S71NS128JA0BAW21@FBGA48 [CX50UN] S71NS128JA0BFW01@FBGA48 [CX50UN]  
S71NS128JA0BFW11@FBGA48 [CX50UN] S71NS128JA0BFW21@FBGA48 [CX50UN]  
S71NS128NA0BJWRN@FBGA56 [CX5066]  
S71NS128NA0BJWRN@FBGA56(ZTE) [CX5183]  
S71NS128NA0BJWSN@FBGA44 [CX5066] S71NS128NB0BJWRN@FBGA56 [CX5066]  
S71NS128NC0BJWRN@FBGA56 [CX5066] S71NS128PA0ZJAGV@FBGA44 [CX5067]  
S71NS128PB0ZJEJR@FBGA56 [CX5066] S71NS128PB0ZJETV@FBGA56 [CX5066]  
S71NS128PB0ZJETV@FBGA56(ZTE) [CX5183]  
S71NS128PC0ZJEJR@FBGA56 [CX5066] S71NS128PC0ZJETV@FBGA56 [CX5066]  
S71NS128RA0AHAGR@FBGA44 [CX5067] S71NS128RA0AHAGV@FBGA44 [CX5067]  
S71NS128RA0AHAJR@FBGA44 [CX5067] S71NS128RA0AHAJV@FBGA44 [CX5067]  
S71NS128RA0ZHAGR@FBGA44 [CX5067] S71NS128RA0ZHAGV@FBGA44 [CX5067]  
S71NS128RA0ZHAJR@FBGA44 [CX5067] S71NS128RA0ZHAJV@FBGA44 [CX5067]  
S71NS256NB0BJWVN@FBGA60 [CX50UN] S71NS256NC0BJWVN@FBGA60 [CX50UN]  
S71NS256PB0ZJEJR@FBGA56 [CX5066] S71NS256PB0ZJETV@FBGA56 [CX5066]  
S71NS256PC0ZJEJR@FBGA56 [CX5066] S71NS256PC0ZJETV@FBGA56 [CX5066]  
S71NS256RB0AHAGR@FBGA44 [CX5067] S71NS256RB0AHAGV@FBGA44 [CX5067]  
S71NS256RB0AHAJR@FBGA44 [CX5067] S71NS256RB0AHAJV@FBGA44 [CX5067]  
S71NS256RB0ZHAGR@FBGA44 [CX5067] S71NS256RB0ZHAGV@FBGA44 [CX5067]  
S71NS256RB0ZHAJR@FBGA44 [CX5067] S71NS256RB0ZHAJV@FBGA44 [CX5067]  
S71NS256RC0ZHKJL@FBGA56 [CX5067] S71NS256RD0ZHEJL@FBGA56 [CX5066]  
S71NS512RD0ZHEJL@FBGA56 [CX5066] S71NS512RD0ZHEKL@FBGA56 [CX5066]  
S71NS512RD0ZHEML@FBGA56 [CX5066] S71PL032J04BAI0B@FBGA56 [CX5045]  
S71PL032J04BAI0F@FBGA56 [CX5045] S71PL032J04BAW0B@FBGA56 [CX5045]  
S71PL032J04BAW0F@FBGA56 [CX5045] S71PL032J04BAW0K@FBGA56 [CX5045]  
S71PL032J04BFI0B@FBGA56 [CX5045] S71PL032J04BFI0F@FBGA56 [CX5045]  
S71PL032J04BFW0B@FBGA56 [CX5045] S71PL032J04BFW0F@FBGA56 [CX5045]  
S71PL032J04BFW0K@FBGA56 [CX5045] S71PL032J08BAE0B@FBGA56 [CX5045]  
S71PL032J08BAI07@FBGA56 [CX5045] S71PL032J08BAW07@FBGA56 [CX5045]  
S71PL032J08BAW0B@FBGA56 [CX5045] S71PL032J08BAW0K@FBGA56 [CX5045]  
S71PL032J08BFE0B@FBGA56 [CX5045] S71PL032J08BFI07@FBGA56 [CX5045]  
S71PL032J08BFW07@FBGA56 [CX5045] S71PL032J08BFW0B@FBGA56 [CX5045]  
S71PL032J08BFW0K@FBGA56 [CX5045] S71PL032J40BAI07@FBGA56 [CX5045]  
S71PL032J40BAW07@FBGA56 [CX5045] S71PL032J40BFI07@FBGA56 [CX5045]  
S71PL032J40BFW07@FBGA56 [CX5045] S71PL032J80BAI05@FBGA56 [CX5045]  
S71PL032J80BAI07@FBGA56 [CX5045] S71PL032J80BAW05@FBGA56 [CX5045]  
S71PL032J80BAW07@FBGA56 [CX5045] S71PL032J80BAW0P@FBGA56 [CX5045]  
S71PL032J80BAWQ7@FBGA56 [CX5045] S71PL032J80BAWQF@FBGA56 [CX5045]  
S71PL032J80BFI05@FBGA56 [CX5045] S71PL032J80BFI07@FBGA56 [CX5045]  
S71PL032J80BFW05@FBGA56 [CX5045] S71PL032J80BFW07@FBGA56 [CX5045]  
S71PL032J80BFW0P@FBGA56 [CX5045] S71PL032J80BFWQ7@FBGA56 [CX5045]  
S71PL032J80BFWQF@FBGA56 [CX5045] S71PL032JA0BAE07@FBGA56 [CX5045]  
S71PL032JA0BAE0F@FBGA56 [CX5045] S71PL032JA0BAI07@FBGA56 [CX5045]  
S71PL032JA0BAI0F@FBGA56 [CX5045] S71PL032JA0BAW07@FBGA56 [CX5045]  
S71PL032JA0BAW0F@FBGA56 [CX5045] S71PL032JA0BAW0Z@FBGA56 [CX5045]  
S71PL032JA0BAWQF@FBGA56 [CX5045] S71PL032JA0BFE07@FBGA56 [CX5045]  
S71PL032JA0BFE0F@FBGA56 [CX5045] S71PL032JA0BFI07@FBGA56 [CX5045]  
S71PL032JA0BFI0F@FBGA56 [CX5045] S71PL032JA0BFW07@FBGA56 [CX5045]  
S71PL032JA0BFW0F@FBGA56 [CX5045] S71PL032JA0BFW0Z@FBGA56 [CX5045]  
S71PL032JA0BFWQF@FBGA56 [CX5045] S71PL064J08BAI0B@FBGA56 [CX5045]  
S71PL064J08BAI0K@FBGA56 [CX5045] S71PL064J08BAI0P@FBGA56 [CX5045]  
S71PL064J08BAI0U@FBGA56 [CX5045] S71PL064J08BAW0B@FBGA56 [CX5045]



S71PL064J08BAW0K@FBGA56 [CX5045] S71PL064J08BAW0P@FBGA56 [CX5045]  
S71PL064J08BAW0U@FBGA56 [CX5045] S71PL064J08BFI0B@FBGA56 [CX5045]  
S71PL064J08BFI0K@FBGA56 [CX5045] S71PL064J08BFI0P@FBGA56 [CX5045]  
S71PL064J08BFI0U@FBGA56 [CX5045] S71PL064J08BFW0B@FBGA56 [CX5045]  
S71PL064J08BFW0K@FBGA56 [CX5045] S71PL064J08BFW0P@FBGA56 [CX5045]  
S71PL064J08BFW0U@FBGA56 [CX5045] S71PL064J0ABAW0B@FBGA56 [CX5045]  
S71PL064J0ABAW0S@FBGA56 [CX5045] S71PL064J0ABFW0B@FBGA56 [CX5045]  
S71PL064J0ABFW0S@FBGA56 [CX5045] S71PL064J80BAI05@FBGA56 [CX5045]  
S71PL064J80BAI07@FBGA56 [CX5045] S71PL064J80BAI0K@FBGA56 [CX5045]  
S71PL064J80BAW05@FBGA56 [CX5045] S71PL064J80BAW07@FBGA56 [CX5045]  
S71PL064J80BAW0K@FBGA56 [CX5045] S71PL064J80BAW0P@FBGA56 [CX5045]  
S71PL064J80BFI05@FBGA56 [CX5045] S71PL064J80BFI07@FBGA56 [CX5045]  
S71PL064J80BFI0K@FBGA56 [CX5045] S71PL064J80BFW05@FBGA56 [CX5045]  
S71PL064J80BFW07@FBGA56 [CX5045] S71PL064J80BFW0K@FBGA56 [CX5045]  
S71PL064J80BFW0P@FBGA56 [CX5045] S71PL064JA0BAI05@FBGA56 [CX5045]  
S71PL064JA0BAI07@FBGA56 [CX5045] S71PL064JA0BAI0P@FBGA56 [CX5045]  
S71PL064JA0BAI0Z@FBGA56 [CX5045] S71PL064JA0BAW05@FBGA56 [CX5045]  
S71PL064JA0BAW07@FBGA56 [CX5045] S71PL064JA0BAW0B@FBGA56 [CX5045]  
S71PL064JA0BAW0P@FBGA56 [CX5045] S71PL064JA0BAW0Z@FBGA56 [CX5045]  
S71PL064JA0BFI05@FBGA56 [CX5045] S71PL064JA0BFI07@FBGA56 [CX5045]  
S71PL064JA0BFI0P@FBGA56 [CX5045] S71PL064JA0BFI0Z@FBGA56 [CX5045]  
S71PL064JA0BFW05@FBGA56 [CX5045] S71PL064JA0BFW07@FBGA56 [CX5045]  
S71PL064JA0BFW0B@FBGA56 [CX5045] S71PL064JA0BFW0P@FBGA56 [CX5045]  
S71PL064JA0BFW0Z@FBGA56 [CX5045] S71PL064JB0BAI07@FBGA56 [CX5045]  
S71PL064JB0BAI0U@FBGA56 [CX5045] S71PL064JB0BAIQB@FBGA56 [CX5045]  
S71PL064JB0BAW07@FBGA56 [CX5045] S71PL064JB0BAW0B@FBGA56 [CX5045]  
S71PL064JB0BAW0U@FBGA56 [CX5045] S71PL064JB0BAWQB@FBGA56 [CX5045]  
S71PL064JB0BFI07@FBGA56 [CX5045] S71PL064JB0BFI0U@FBGA56 [CX5045]  
S71PL064JB0BFIQB@FBGA56 [CX5045] S71PL064JB0BFW07@FBGA56 [CX5045]  
S71PL064JB0BFW0B@FBGA56 [CX5045] S71PL064JB0BFW0U@FBGA56 [CX5045]  
S71PL064JB0BFWQB@FBGA56 [CX5045] S71PL127JA0BAI9P@FBGA64 [CX5001]  
S71PL127JA0BAI9Z@FBGA64 [CX5001] S71PL127JA0BAW9P@FBGA64 [CX5001]  
S71PL127JA0BAW9Z@FBGA64 [CX5001] S71PL127JA0BFI9P@FBGA64 [CX5001]  
S71PL127JA0BFI9Z@FBGA64 [CX5001] S71PL127JA0BFW9P@FBGA64 [CX5001]  
S71PL127JA0BFW9Z@FBGA64 [CX5001] S71PL127JB0BAI97@FBGA64 [CX5001]  
S71PL127JB0BAI9U@FBGA64 [CX5001] S71PL127JB0BAI9Z@FBGA64 [CX5001]  
S71PL127JB0BAIQB@FBGA64 [CX5001] S71PL127JB0BAW97@FBGA64 [CX5001]  
S71PL127JB0BAW9B@FBGA64 [CX5001] S71PL127JB0BAW9U@FBGA64 [CX5001]  
S71PL127JB0BAW9Z@FBGA64 [CX5001] S71PL127JB0BAWQB@FBGA64 [CX5001]  
S71PL127JB0BFI97@FBGA64 [CX5001] S71PL127JB0BFI9U@FBGA64 [CX5001]  
S71PL127JB0BFI9Z@FBGA64 [CX5001] S71PL127JB0BFIQB@FBGA64 [CX5001]  
S71PL127JB0BFW97@FBGA64 [CX5001] S71PL127JB0BFW9B@FBGA64 [CX5001]  
S71PL127JB0BFW9U@FBGA64 [CX5001] S71PL127JB0BFW9Z@FBGA64 [CX5001]  
S71PL127JB0BFWQB@FBGA64 [CX5001] S71PL127JCB0BAI97@FBGA64 [CX5001]  
S71PL127JCB0BAI9U@FBGA64 [CX5001] S71PL127JCB0BAI9Z@FBGA64 [CX5001]  
S71PL127JCB0BAW97@FBGA64 [CX5001] S71PL127JCB0BAW9B@FBGA64 [CX5001]  
S71PL127JCB0BAW9U@FBGA64 [CX5001] S71PL127JCB0BAW9Z@FBGA64 [CX5001]  
S71PL127JCB0BFI97@FBGA64 [CX5001] S71PL127JCB0BFI9U@FBGA64 [CX5001]  
S71PL127JCB0BFI9Z@FBGA64 [CX5001] S71PL127JCB0BFW97@FBGA64 [CX5001]  
S71PL127JCB0BFW9B@FBGA64 [CX5001] S71PL127JCB0BFW9U@FBGA64 [CX5001]  
S71PL127JCB0BFW9Z@FBGA64 [CX5001] S71PL127NB0HAW4B@FBGA64 [CX5001]  
S71PL127NB0HAW4U@FBGA64 [CX5001] S71PL127NB0HAW4Z@FBGA64 [CX5001]  
S71PL127NB0HFW4B@FBGA64 [CX5001] S71PL127NB0HFW4U@FBGA64 [CX5001]  
S71PL127NB0HFW4Z@FBGA64 [CX5001] S71PL127NB0HHW4U@FBGA64 [CX5001]  
S71PL127NB0HHW4U@FBGA64(XW) [CX5005]  
S71PL127NC0HAW4B@FBGA64 [CX5001] S71PL127NC0HAW4U@FBGA64 [CX5001]  
S71PL127NC0HFW4B@FBGA64 [CX5001] S71PL127NC0HFW4U@FBGA64 [CX5001]  
S71PL129JA0BAI9P@FBGA64 [CX5001] S71PL129JA0BAW9P@FBGA64 [CX5001]  
S71PL129JA0BFI9P@FBGA64 [CX5001] S71PL129JA0BFW9P@FBGA64 [CX5001]



S71PL256ND0HAW5B@FBGA84 [CX5001] S71PL256ND0HAW5U@FBGA84 [CX5001]  
S71PL256ND0HFW5B@FBGA84 [CX5001] S71PL256ND0HFW5U@FBGA84 [CX5001]  
S71PL512ND0JAW5B@FBGA84 [CX5001] S71PL512ND0JFW5B@FBGA84 [CX5001]  
S71VS032K80ZJK01@FBGA56 [CX5094] S71VS032K80ZJK03@FBGA56 [CX5094]  
S71VS032KA0ZJK09@FBGA56 [CX5094] S71VS032KA0ZJK0B@FBGA56 [CX5094]  
S71VS032KA0ZJK11@FBGA56 [CX5094] S71VS032KA0ZJK13@FBGA56 [CX5094]  
S71VS032KA0ZJK19@FBGA56 [CX5094] S71VS032KA0ZJK1B@FBGA56 [CX5094]  
S71VS064KA0ZJK01@FBGA56 [CX5094] S71VS064KA0ZJK03@FBGA56 [CX5094]  
S71VS064KA0ZJK09@FBGA56 [CX5094] S71VS064KA0ZJK0B@FBGA56 [CX5094]  
S71VS064KA0ZJK11@FBGA56 [CX5094] S71VS064KA0ZJK13@FBGA56 [CX5094]  
S71VS064KA0ZJK19@FBGA56 [CX5094] S71VS064KA0ZJK1B@FBGA56 [CX5094]  
S71VS064RB0AHT0L@FBGA52 [CX5199] S71VS064RB0AHT0M@FBGA52 [CX5199]  
S71VS064RB0AHT3L@FBGA52 [CX5199] S71VS064RB0AHT4L@FBGA52 [CX5199]  
S71VS064RB0AHT8L@FBGA52 [CX5199] S71VS064RB0AHT8M@FBGA52 [CX5199]  
S71VS064RB0AHTBL@FBGA52 [CX5199] S71VS064RB0AHTCL@FBGA52 [CX5199]  
S71VS128RB0AHK0L@FBGA56 [CX5094] S71VS128RB0AHK2L@FBGA56 [CX5094]  
S71VS128RB0AHK4S@FBGA56 [CX5066] S71VS128RB0AHK8L@FBGA56 [CX5094]  
S71VS128RB0AHKAL@FBGA56 [CX5094] S71VS128RC0AHK20@FBGA56 [CX5094]  
S71VS128RC0AHK3L@FBGA56(wdk) [CX5094]  
S71VS128RC0AHK4L@FBGA56 [CX5094]  
S71VS128RC0AHK4L@FBGA56(spec) [CX5094]  
S71VS128RC0AHK4L@FBGA56(wdk) [CX5094]  
S71VS128RC0AHKCL@FBGA56 [CX5094] S71VS128RC0ZHK20@FBGA56 [CX5094]  
S71VS128RC0ZHK24@FBGA56 [CX5094] S71VS128RC0ZHKA0@FBGA56 [CX5094]  
S71VS128RC0ZHKA4@FBGA56 [CX5094] S71VS256RC0AHK4L@FBGA56 [CX5094]  
S71VS256RC0AHKCL@FBGA56 [CX5094] S71VS256RC0ZHK20@FBGA56 [CX5094]  
S71VS256RC0ZHK24@FBGA56 [CX5094] S71VS256RC0ZHKA0@FBGA56 [CX5094]  
S71VS256RC0ZHKA4@FBGA56 [CX5094] S71VS256RD0AHK3C@FBGA56 [CX5094]  
S71VS256RD0AHK3L@FBGA56 [CX5094] S71VS256RD0AHKBC@FBGA56 [CX5094]  
S71VS256RD0AHKBL@FBGA56 [CX5094] S71VS256RD0ZHE40@FBGA56 [CX5066]  
S71VS256RD0ZHE40@FBGA56(ZTE) [CX5183]  
S71VS256RD0ZHE44@FBGA56 [CX5066]  
S71VS256RD0ZHEC0(BN)@FBGA56 [CX5066]  
S71VS256RD0ZHEC0@FBGA56 [CX5066] S71VS256RD0ZHEC4@FBGA56 [CX5066]  
S71WS064JA0BAI2A@FBGA80 [CX5052] S71WS064JA0BAI2Y@FBGA80 [CX5052]  
S71WS064JA0BAW2A@FBGA80 [CX5052] S71WS064JA0BAW2Y@FBGA80 [CX5052]  
S71WS064JA0BFI2A@FBGA80 [CX5052] S71WS064JA0BFI2Y@FBGA80 [CX5052]  
S71WS064JA0BFW2A@FBGA80 [CX5052] S71WS064JA0BFW2Y@FBGA80 [CX5052]  
S71WS064JB0BAI2A@FBGA80 [CX5052] S71WS064JB0BAI2Y@FBGA80 [CX5052]  
S71WS064JB0BAW2A@FBGA80 [CX5052] S71WS064JB0BAW2Y@FBGA80 [CX5052]  
S71WS064JB0BFI2A@FBGA80 [CX5052] S71WS064JB0BFI2Y@FBGA80 [CX5052]  
S71WS064JB0BFW2A@FBGA80 [CX5052] S71WS064JB0BFW2Y@FBGA80 [CX5052]  
S71WS128HC0BAWA7@FBGA88 [CX5001] S71WS128HC0BAWAB@FBGA88 [CX5001]  
S71WS128HC0BFWA7@FBGA88 [CX5001] S71WS128HC0BFWAB@FBGA88 [CX5001]  
S71WS128JA0BAIAA@FBGA84 [CX5001] S71WS128JA0BAIAJ@FBGA84 [CX5001]  
S71WS128JA0BAWAA@FBGA84 [CX5001] S71WS128JA0BAWAJ@FBGA84 [CX5001]  
S71WS128JA0BFIAA@FBGA84 [CX5001] S71WS128JA0BFIAJ@FBGA84 [CX5001]  
S71WS128JA0BFWAA@FBGA84 [CX5001] S71WS128JA0BFWAJ@FBGA84 [CX5001]  
S71WS128JB0BAE9Y@FBGA84 [CX5001] S71WS128JB0BAIAA@FBGA84 [CX5001]  
S71WS128JB0BAIAJ@FBGA84 [CX5001] S71WS128JB0BAIAY@FBGA84 [CX5001]  
S71WS128JB0BAWAA@FBGA84 [CX5001] S71WS128JB0BAWAJ@FBGA84 [CX5001]  
S71WS128JB0BAWAY@FBGA84 [CX5001] S71WS128JB0BFIAA@FBGA84 [CX5001]  
S71WS128JB0BFIAJ@FBGA84 [CX5001] S71WS128JB0BFIAJ@FBGA84 [CX5001]  
S71WS128JB0BFWAA@FBGA84 [CX5001] S71WS128JB0BFWAJ@FBGA84 [CX5001]  
S71WS128JB0BFWAY@FBGA84 [CX5001] S71WS128JC0BAE9A@FBGA84 [CX5001]  
S71WS128JC0BAE9Y@FBGA84 [CX5001] S71WS128JC0BAIA6@FBGA84 [CX5001]  
S71WS128JC0BAIAA@FBGA84 [CX5001] S71WS128JC0BAIAJ@FBGA84 [CX5001]  
S71WS128JC0BAIAY@FBGA84 [CX5001] S71WS128JC0BAWA6@FBGA84 [CX5001]  
S71WS128JC0BAWAA@FBGA84 [CX5001] S71WS128JC0BAWAJ@FBGA84 [CX5001]





S71WS512ND0BAWE2@FBGA84 [CX5054]	S71WS512ND0BAWE3@FBGA84 [CX5054]
S71WS512ND0BAWE6@FBGA84 [CX5054]	S71WS512ND0BAWE7@FBGA84 [CX5054]
S71WS512ND0BAWEH@FBGA84 [CX5054]	S71WS512ND0BAWEJ@FBGA84 [CX5054]
S71WS512ND0BAWEK@FBGA84 [CX5054]	S71WS512ND0BAWEM@FBGA84 [CX5054]
S71WS512ND0BAWEN@FBGA84 [CX5054]	S71WS512ND0BAWEP@FBGA84 [CX5054]
S71WS512ND0BFIE3@FBGA84 [CX5054]	S71WS512ND0BFIE7@FBGA84 [CX5054]
S71WS512ND0BFIEK@FBGA84 [CX5054]	S71WS512ND0BFIEP@FBGA84 [CX5054]
S71WS512ND0BFWE2@FBGA84 [CX5054]	S71WS512ND0BFWE3@FBGA84 [CX5054]
S71WS512ND0BFWE6@FBGA84 [CX5054]	S71WS512ND0BFWE7@FBGA84 [CX5054]
S71WS512ND0BFWEH@FBGA84 [CX5054]	S71WS512ND0BFWEJ@FBGA84 [CX5054]
S71WS512ND0BFWEK@FBGA84 [CX5054]	S71WS512ND0BFWEM@FBGA84 [CX5054]
S71WS512ND0BFWEN@FBGA84 [CX5054]	S71WS512ND0BFWEP@FBGA84 [CX5054]
S71WS512PC0HF3S2@FBGA84 [CX5001]	S71WS512PC0HF3SL@FBGA84 [CX5001]
S71WS512PC0HF3SR@FBGA84 [CX5001]	S71WS512PC0HF3SV@FBGA84 [CX5001]
S71WS512PC0HF3SW@FBGA84 [CX5001]	S71WS512PD0HF3HR@FBGA84 [CX5001]
S71WS512PD0HF3SL@FBGA84 [CX5001]	S71WS512PD0HF3SR@FBGA84 [CX5001]
S71WS512PD0HF3TL@FBGA84 [CX5001]	S71WS512PD0HF3TR@FBGA84 [CX5001]
S71WS512PD0HH3SL@FBGA84 [CX5001]	S71WS512PD0HH3SR@FBGA84 [CX5001]
S71WS512PD0HH3YL@FBGA84 [CX5001]	S71WS512PD0HH3YR@FBGA84 [CX5001]
S71WS512PD0HH3YV@FBGA84 [CX5001]	S71WS512RD0HH309@FBGA84 [CX5001]
S71WS512RD0HH30A@FBGA84 [CX5001]	S71WS512RD0HH329@FBGA84 [CX5001]
S71WS512RD0HH32A@FBGA84 [CX5001]	S75PL127JBDBAWKB@FBGA84 [CX5054]
S75PL127JBDBAWKU@FBGA84 [CX5054]	S75PL127JBDBFWKB@FBGA84 [CX5054]
S75PL127JBDBFWKU@FBGA84 [CX5054]	S75PL127JBEBAWKB@FBGA84 [CX5054]
S75PL127JBEBAWKU@FBGA84 [CX5054]	S75PL127JBEBFWKB@FBGA84 [CX5054]
S75PL127JBEBFWKU@FBGA84 [CX5054]	S75PL127JBFBAWKB@FBGA84 [CX5054]
S75PL127JBFBFWKU@FBGA84 [CX5054]	S75PL127JBFBFWKB@FBGA84 [CX5054]
S75PL127JBFBFWKU@FBGA84 [CX5054]	S75PL127JCDBAWKB@FBGA84 [CX5054]
S75PL127JCDBAWKU@FBGA84 [CX5054]	S75PL127JCDBFWKB@FBGA84 [CX5054]
S75PL127JCDBFWKU@FBGA84 [CX5054]	S75PL127JCEBAWKB@FBGA84 [CX5054]
S75PL127JCEBAWKU@FBGA84 [CX5054]	S75PL127JCEBFWKB@FBGA84 [CX5054]
S75PL127JCEBFWKU@FBGA84 [CX5054]	S75PL127JCFBAWKB@FBGA84 [CX5054]
S75PL127JCFBAWKU@FBGA84 [CX5054]	S75PL127JCFBFWKB@FBGA84 [CX5054]
S75PL127JCFBFWKU@FBGA84 [CX5054]	S98GL064NB0HI001@FBGA56 [CX5045]
S98GL064NB0HI002@FBGA56 [CX5045]	S98GL128PB0HW020@FBGA64 [CX5079]
S98GL128PB0HW021@FBGA64 [CX5079]	S98NS032JA0FW001@FBGA88 [CX5001]
S98NS128NB0FW001@FBGA88 [CX5001]	S98NS256PB0HW001@FBGA56 [CX5066]
S98WS01GPE0HW020@FBGA88 [CX5001]	S98WS01GPE0HW022@FBGA88 [CX5001]
S98WS01GPE0HW023@FBGA88 [CX5001]	S98WS128NB0FW001@FBGA88 [CX5001]
S98WS256PC0FW001@FBGA88 [CX5001]	S98WS512PD0FW004@FBGA88 [CX5001]
S98WS512PD0FW006@FBGA88 [CX5001]	S98WS512PE0FW002@FBGA88 [CX5001]
S98WS512PE0FW010@FBGA88 [CX5001]	S98WS512PE0FW013@FBGA88 [CX5001]
S99-50001(S29WS256N)@FBGA88 [CX5001]	
S99-50003(S29WS256N)@FBGA88 [CX5001]	
S99-50070(S29GL512N)@TSOP56 [CX1011]	
S99-50073(S29WS256N)@FBGA88 [CX5001]	
S99-50085(S29WS256N)@FBGA88 [CX5001]	
S99-50268@FBGA64 [CX5103]	S99-50282@FBGA64 [CX5103]
S99-50291@FBGA64 [CX5103]	S99GL128S0110@FBGA64 [CX5074]
S99PL193JB0BAEFC@FBGA73 [CX5072]	S99PL193JB0BAEUC@FBGA73 [CX5072]
S99PL193JB0BAWFC@FBGA73 [CX5072]	S99PL193JB0BAWUC@FBGA73 [CX5072]
S99PL193JC0BAEFC@FBGA73 [CX5072]	S99PL193JC0BAEUC@FBGA73 [CX5072]
S99PL193JC0BAWFC@FBGA73 [CX5072]	S99PL193JC0BAWUC@FBGA73 [CX5072]

**MICROCONTROLLER**

MB96F673AAPMC [CX3064]	MB96F673AAPMC1 [CX3011]
MB96F673ABPMC [CX3064]	MB96F673ABPMC1 [CX3011]
MB96F673RAPMC [CX3064]	MB96F673RAPMC1 [CX3011]

MB96F673RBPMC [CX3064]  
MB96F675AAPMC [CX3064]  
MB96F675ABPMC [CX3064]  
MB96F675RAPMC [CX3064]  
MB96F675RBPMC [CX3064]  
MB96F683AAPMC [CX3016]  
MB96F683RAPMC [CX3016]  
MB96F685AAPMC [CX3016]  
MB96F685RAPMC [CX3016]

MB96F673RBPMC1 [CX3011]  
MB96F675AAPMC1 [CX3011]  
MB96F675ABPMC1 [CX3011]  
MB96F675RAPMC1 [CX3011]  
MB96F675RBPMC1 [CX3011]  
MB96F683ABPMC [CX3016]  
MB96F683RBPMC [CX3016]  
MB96F685ABPMC [CX3016]  
MB96F685RBPMC [CX3016]

## SSSC

### MICROCONTROLLER

SSU7301 [CX0001]  
SSU7301@TQFP44 [CX3002]

SSU7301@PLCC44 [CX2044]

## SST

### E (E) PROM/FRAM/NVRAM

SST25LF010@SOIC8(4.0) [CX1045]  
SST25LF010@WSON8 [CX4005]  
SST25LF010A@SOIC8(5.4) [CX1044]  
SST25LF010A@WSON8 [CX4005]  
SST25LF016A@SOIC8(4.0) [CX1045#1]  
SST25LF016A@SOIC8(5.4) [CX1044#1]  
SST25LF016A@WSON8 [CX4005#1]  
SST25LF016B@SOIC8(4.0) [CX1045#1]  
SST25LF016B@SOIC8(5.4) [CX1044#1]  
SST25LF016B@WSON8 [CX4005#1]  
SST25LF020@SOIC8(5.4) [CX1044]  
SST25LF020A@SOIC8(4.0) [CX1045]  
SST25LF020A@WSON8 [CX4005]  
SST25LF040@SOIC8(5.4) [CX1044]  
SST25LF040A@SOIC8(4.0) [CX1045]  
SST25LF040A@WSON8 [CX4005]  
SST25LF080@SOIC8(5.4) [CX1044]  
SST25LF080A@SOIC8(4.0) [CX1045]  
SST25LF080A@WSON8 [CX4005]  
SST25PF020B@USON8 [CX4002#1]  
SST25PF040B@SOIC8[150mil] [CX1045#1]  
SST25PF040B@SOIC8[200mil] [CX1044#1]  
SST25PF040B@WSON8 [CX4005#1]  
SST25PF080B@SOIC8[150mil] [CX1045#1]  
SST25PF080B@SOIC8[200mil] [CX1044#1]  
SST25PF080B@WSON8 [CX4005#1]  
SST25VF010@SOIC8(5.4) [CX1044]  
SST25VF010A@SOIC8(4.0) [CX1045]  
SST25VF010A@WSON8 [CX4005]  
SST25VF016B@SOIC8(4.0) [CX1045#1]  
SST25VF016B@SOIC8(5.4) [CX1044#1]  
SST25VF016B@WSON8 [CX4005#1]  
SST25VF020@SOIC8(5.4) [CX1044]  
SST25VF020B@SOIC8(4.0) [CX1045#1]  
SST25VF020B@SOIC8(5.4) [CX1044#1]  
SST25VF020B@WSON8 [CX4005#1]  
SST25VF032B@SOIC8(4.0) [CX1045#1]  
SST25LF010@SOIC8(5.4) [CX1044]  
SST25LF010A@SOIC8(4.0) [CX1045]  
SST25LF010A@WSON8 [CX4005]  
SST25LF020@SOIC8(4.0) [CX1045]  
SST25LF020@WSON8 [CX4005]  
SST25LF020A@SOIC8(5.4) [CX1044]  
SST25LF040@SOIC8(4.0) [CX1045]  
SST25LF040@WSON8 [CX4005]  
SST25LF040A@SOIC8(5.4) [CX1044]  
SST25LF080@SOIC8(4.0) [CX1045]  
SST25LF080@WSON8 [CX4005]  
SST25LF080A@SOIC8(5.4) [CX1044]  
SST25PF020B@SOIC8 [CX1045#1]  
SST25PF020B@WSON8 [CX4005#1]  
SST25VF010@SOIC8(4.0) [CX1045]  
SST25VF010@WSON8 [CX4005]  
SST25VF010A@SOIC8(5.4) [CX1044]  
SST25VF020@SOIC8(4.0) [CX1045]  
SST25VF020@WSON8 [CX4005]  
SST25VF032B@SOIC16 [CX1033#1]

SST25VF032B@SOIC8(5.4) [CX1044#1]  
SST25VF032B@WSON8 [CX4005#1]  
SST25VF040@SOIC8(5.4) [CX1044]  
SST25VF040B@SOIC8(4.0) [CX1045#1]  
SST25VF040B@SOIC8(5.4) [CX1044#1]  
SST25VF040B@WSON8 [CX4005#1]  
SST25VF064C@SOIC8 [CX1044#1]  
SST25VF080@SOIC8(4.0) [CX1045]  
SST25VF080@WSON8 [CX4005]  
SST25VF080B@SOIC8(4.0) [CX1045#1]  
SST25VF080B@SOIC8(5.4) [CX1044#1]  
SST25VF080B@WSON8 [CX4005#1]  
SST25VF512@SOIC8(5.4) [CX1044]  
SST25VF512A@SOIC8(4.0) [CX1045]  
SST25VF512A@WSON8 [CX4005]  
SST25WF010@SOIC8(5.4) [CX1044]  
SST25WF020@SOIC8(4.0) [CX1045]  
SST25WF020@WSON8 [CX4005]  
SST25WF040@SOIC8(5.4) [CX1044]  
SST25WF080@SOIC8(4.0) [CX1045]  
SST25WF080@WSON8 [CX4005]  
SST25WF512@SOIC8(5.4) [CX1044]  
SST26VF016@SOIC8 [CX1044#1]  
SST26VF032@SOIC8 [CX1045#1]  
SST27SF010 [CX0001]  
SST27SF010@TSOP32 [CX1002]  
SST27SF020@PLCC32 [CX2032]  
SST27SF256 [CX0001]  
SST27SF256@VSOP32 [CX1003]  
SST27SF512@PLCC32 [CX2032]  
SST27VF010 [CX0001]  
SST27VF010@TSOP32 [CX1002]  
SST27VF020@PLCC32 [CX2032]  
SST27VF040 [CX0001]  
SST27VF040@TSOP32 [CX1002]  
SST27VF256@PLCC32 [CX2032]  
SST27VF512 [CX0001]  
SST27VF512@VSOP32 [CX1003]  
SST28EE011@PLCC32 [CX2032]  
SST28EE011 [CX0001]  
SST28LE011@TSOP32 [CX1002]  
SST28LF040@PLCC32 [CX2032]  
SST28SF040 [CX0001]  
SST28SF040@TSOP32 [CX1002]  
SST28SF040A@PLCC32 [CX2032]  
SST28VE011 [CX0001]  
SST28VE011@TSOP32 [CX1002]  
SST28VF040@PLCC32 [CX2032]  
SST28VF040A [CX0001]  
SST28VF040A@TSOP32 [CX1002]  
SST29EE010@PLCC32 [CX2032]  
SST29EE010@VSOP32 [CX1003]  
SST29EE020@PLCC32 [CX2032]  
SST29EE020@VSOP32 [CX1003]  
SST29EE512@PLCC32 [CX2032]  
SST29EE512@VSOP32 [CX1003]  
SST29LE010@PLCC32 [CX2032]  
SST29LE010@VSOP32 [CX1003]  
SST29LE020@PLCC32 [CX2032]  
SST25VF040@SOIC8(4.0) [CX1045]  
SST25VF040@WSON8 [CX4005]  
SST25VF064C@SOIC16 [CX1033#1]  
SST25VF064C@WSON8 [CX4006#1]  
SST25VF080@SOIC8(5.4) [CX1044]  
SST25VF512@SOIC8(4.0) [CX1045]  
SST25VF512@WSON8 [CX4005]  
SST25VF512A@SOIC8(5.4) [CX1044]  
SST25WF010@SOIC8(4.0) [CX1045]  
SST25WF010@WSON8 [CX4005]  
SST25WF020@SOIC8(5.4) [CX1044]  
SST25WF040@SOIC8(4.0) [CX1045]  
SST25WF040@WSON8 [CX4005]  
SST25WF080@SOIC8(5.4) [CX1044]  
SST25WF512@SOIC8(4.0) [CX1045]  
SST25WF512@WSON8 [CX4005]  
SST26VF016@WSON8 [CX4005#1]  
SST26VF032@WSON8 [CX4005#1]  
SST27SF010@PLCC32 [CX2032]  
SST27SF020 [CX0001]  
SST27SF020@TSOP32 [CX1002]  
SST27SF256@PLCC32 [CX2032]  
SST27SF512 [CX0001]  
SST27SF512@VSOP32 [CX1003]  
SST27VF010@PLCC32 [CX2032]  
SST27VF020 [CX0001]  
SST27VF020@TSOP32 [CX1002]  
SST27VF040@PLCC32 [CX2032]  
SST27VF256 [CX0001]  
SST27VF256@VSOP32 [CX1003]  
SST27VF512@PLCC32 [CX2032]  
SST28EE011 [CX0001]  
SST28EE011@TSOP32 [CX1002]  
SST28LE011@PLCC32 [CX2032]  
SST28LF040 [CX0001]  
SST28LF040@TSOP32 [CX1002]  
SST28SF040@PLCC32 [CX2032]  
SST28SF040A [CX0001]  
SST28SF040A@TSOP32 [CX1002]  
SST28VE011@PLCC32 [CX2032]  
SST28VF040 [CX0001]  
SST28VF040@TSOP32 [CX1002]  
SST28VF040A@PLCC32 [CX2032]  
SST29EE010 [CX0001]  
SST29EE010@TSOP32 [CX1002]  
SST29EE020 [CX0001]  
SST29EE020@TSOP32 [CX1002]  
SST29EE512 [CX0001]  
SST29EE512@TSOP32 [CX1002]  
SST29LE010 [CX0001]  
SST29LE010@TSOP32 [CX1002]  
SST29LE020 [CX0001]  
SST29LE020@TSOP32 [CX1002]



SST29LE020@VSOP32 [CX1003]  
SST29LE512@PLCC32 [CX2032]  
SST29LE512@VSOP32 [CX1003]  
SST29SF010@PLCC32 [CX2032]  
SST29SF020 [CX0001]  
SST29SF020@VSOP32 [CX1003]  
SST29SF040@PLCC32 [CX2032]  
SST29SF512 [CX0001]  
SST29SF512@VSOP32 [CX1003]  
SST29VE010@PLCC32 [CX2032]  
SST29VE010@VSOP32 [CX1003]  
SST29VE020@PLCC32 [CX2032]  
SST29VE020@VSOP32 [CX1003]  
SST29VE512@PLCC32 [CX2032]  
SST29VE512@VSOP32 [CX1003]  
SST29VF010@PLCC32 [CX2032]  
SST29VF020 [CX0001]  
SST29VF020@VSOP32 [CX1003]  
SST29VF040@PLCC32 [CX2032]  
SST29VF512 [CX0001]  
SST29VF512@VSOP32 [CX1003]  
SST31LF021E@VSOP32 [CX1003]  
SST31LF041A@VSOP32 [CX1003]  
SST31LF043A@VSOP32 [CX1003]  
SST32HF162@TSOP48 [CX1004]  
SST32HF1621C@LFBGA63 [CX5005]  
SST32HF1622C@LFBGA63 [CX5005]  
SST32HF164@TSOP48 [CX1004]  
SST32HF1641@LFBGA63 [CX5005]  
SST32HF1641C@LFBGA63 [CX5005]  
SST32HF1642@FBGA63 [CX5005]  
SST32HF1642C@FBGA63 [CX5005]  
SST32HF1681@LFBGA63 [CX5005]  
SST32HF1682@LFBGA63 [CX5005]  
SST32HF201@LFBGA48 [CX5002]  
SST32HF324@LFBGA62 [CX5005]  
SST32HF324@TFBGA63 [CX5005]  
SST32HF3241@LFBGA63 [CX5005]  
SST32HF3241C@LFBGA63 [CX5005]  
SST32HF3242@FBGA63 [CX5005]  
SST32HF3242C@FBGA63 [CX5005]  
SST32HF324C@LFBGA62 [CX5005]  
SST32HF324C@TFBGA63 [CX5005]  
SST32HF328@LFBGA63 [CX5005]  
SST32HF3281@LFBGA62 [CX5005]  
SST32HF3281C@LFBGA62 [CX5005]  
SST32HF3282@FBGA62 [CX5005]  
SST32HF3282C@FBGA62 [CX5005]  
SST32HF3284@FBGA56 [CX5005]  
SST32HF328C@LFBGA63 [CX5005]  
SST32HF32A1@LFBGA62 [CX5005]  
SST32HF32A4@FBGA56 [CX5005]  
SST32HF401@LFBGA48 [CX5002]  
SST32HF64161@LFBGA63 [CX5005]  
SST32HF64161C@LFBGA63 [CX5005]  
SST32HF6481@LFBGA63 [CX5005]  
SST32HF6481C@LFBGA63 [CX5005]  
SST32HF6482@FBGA63 [CX5005]  
SST32HF6482C@FBGA63 [CX5005]

SST29LE512 [CX0001]  
SST29LE512@TSOP32 [CX1002]  
SST29SF010 [CX0001]  
SST29SF010@VSOP32 [CX1003]  
SST29SF020@PLCC32 [CX2032]  
SST29SF040 [CX0001]  
SST29SF040@VSOP32 [CX1003]  
SST29SF512@PLCC32 [CX2032]  
SST29VE010 [CX0001]  
SST29VE010@TSOP32 [CX1002]  
SST29VE020 [CX0001]  
SST29VE020@TSOP32 [CX1002]  
SST29VE512 [CX0001]  
SST29VE512@TSOP32 [CX1002]  
SST29VF010 [CX0001]  
SST29VF010@VSOP32 [CX1003]  
SST29VF020@PLCC32 [CX2032]  
SST29VF040 [CX0001]  
SST29VF040@VSOP32 [CX1003]  
SST29VF512@PLCC32 [CX2032]  
SST31LF021@VSOP32 [CX1003]  
SST31LF041@TSOP40 [CX1005]  
SST31LF043@TSOP40 [CX1005]  
SST32HF162@LFBGA48 [CX5004]  
SST32HF1621C@LFBGA62 [CX5005]  
SST32HF1622C@LFBGA62 [CX5005]  
SST32HF164@LFBGA48 [CX5004]  
SST32HF1641@LFBGA62 [CX5005]  
SST32HF1641C@LFBGA62 [CX5005]  
SST32HF1642@FBGA62 [CX5005]  
SST32HF1642C@FBGA62 [CX5005]  
SST32HF1681@LFBGA62 [CX5005]  
SST32HF1682@LFBGA62 [CX5005]  
SST32HF200@LFBGA48 [CX5002]  
SST32HF202@LFBGA48 [CX5002]  
SST32HF324@LFBGA63 [CX5005]  
SST32HF3241@LFBGA62 [CX5005]  
SST32HF3241C@LFBGA62 [CX5005]  
SST32HF3242@FBGA62 [CX5005]  
SST32HF3242C@FBGA62 [CX5005]  
SST32HF3244C@FBGA56 [CX5005]  
SST32HF324C@LFBGA63 [CX5005]  
SST32HF328@LFBGA62 [CX5005]  
SST32HF328@TFBGA63 [CX5005]  
SST32HF3281@LFBGA63 [CX5005]  
SST32HF3281C@LFBGA63 [CX5005]  
SST32HF3282@FBGA63 [CX5005]  
SST32HF3282C@FBGA63 [CX5005]  
SST32HF328C@LFBGA62 [CX5005]  
SST32HF328C@TFBGA63 [CX5005]  
SST32HF32A1@LFBGA63 [CX5005]  
SST32HF400@LFBGA48 [CX5002]  
SST32HF402@LFBGA48 [CX5002]  
SST32HF64161@LFBGA64 [CX5005]  
SST32HF64161C@LFBGA64 [CX5005]  
SST32HF6481@LFBGA64 [CX5005]  
SST32HF6481C@LFBGA64 [CX5005]  
SST32HF6482@FBGA64 [CX5005]  
SST32HF6482C@FBGA64 [CX5005]

SST32HF64A1@FBGA63 [CX5005]                   SST32HF64A1@FBGA64 [CX5005]  
SST32HF64A2@FBGA56 [CX5005]                   SST32HF64A2@FBGA63 [CX5005]  
SST32HF64A2@FBGA64 [CX5005]                   SST32HF64B1@FBGA63 [CX5005]  
SST32HF64B1@FBGA64 [CX5005]                   SST32HF64B2@FBGA63 [CX5005]  
SST32HF64B2@FBGA64 [CX5005]                   SST32HF802@LBGA48 [CX5004]  
SST34HF1601B@LFBGA56 [CX5005]                SST34HF1601B@TSOP48 [CX1004]  
SST34HF1601C@FBGA56 [CX5005]                SST34HF1601C@FBGA62 [CX5005]  
SST34HF1602C@FBGA56 [CX5005]                SST34HF1602C@FBGA62 [CX5005]  
SST34HF1621@LFBGA56 [CX5005]                SST34HF1621A@LFBGA56 [CX5005]  
SST34HF1621A@LFBGA62 [CX5005]                SST34HF1621C@FBGA56 [CX5005]  
SST34HF1621C@FBGA62 [CX5005]                SST34HF1621S@FBGA56 [CX5005]  
SST34HF1622@LFBGA56 [CX5005]                SST34HF1622C@FBGA56 [CX5005]  
SST34HF1622C@FBGA62 [CX5005]                SST34HF1622S@FBGA56 [CX5005]  
SST34HF162C@LBGA48 [CX5004]                 SST34HF162G@LBGA48 [CX5004]  
SST34HF162G@LFBGA48 [CX5002]                SST34HF1641@LFBGA56 [CX5005]  
SST34HF1641A@LFBGA56 [CX5005]                SST34HF1641A@LFBGA62 [CX5005]  
SST34HF1641C@FBGA56 [CX5005]                SST34HF1641C@FBGA62 [CX5005]  
SST34HF1641D@FBGA56 [CX5005]                SST34HF1641D@FBGA62 [CX5005]  
SST34HF1641J@FBGA56 [CX5005]                SST34HF1641J@FBGA62 [CX5005]  
SST34HF1641S@FBGA56 [CX5005]                SST34HF1642@LFBGA56 [CX5005]  
SST34HF1642C@FBGA56 [CX5005]                SST34HF1642C@FBGA62 [CX5005]  
SST34HF1642D@FBGA56 [CX5005]                SST34HF1642D@FBGA62 [CX5005]  
SST34HF1642S@FBGA56 [CX5005]                SST34HF164C@LBGA48 [CX5004]  
SST34HF164G@LBGA48 [CX5004]                 SST34HF164G@LFBGA48 [CX5002]  
SST34HF1681@LFBGA56 [CX5005]                SST34HF1681@LFBGA62 [CX5005]  
SST34HF1681D@FBGA56 [CX5005]                SST34HF1681D@FBGA62 [CX5005]  
SST34HF1681J@FBGA56 [CX5005]                SST34HF1681J@FBGA62 [CX5005]  
SST34HF1682D@FBGA56 [CX5005]                SST34HF1682D@FBGA62 [CX5005]  
SST34HF3223B@FBGA56 [CX5005]                SST34HF3243B@FBGA56 [CX5005]  
SST34HF3243C@FBGA56 [CX5005]                SST34HF3243C@FBGA62 [CX5005]  
SST34HF3244@FBGA56 [CX5005]                 SST34HF3244@FBGA62 [CX5005]  
SST34HF3244C@FBGA56 [CX5005]                SST34HF3244C@FBGA62 [CX5005]  
SST34HF3282@FBGA56 [CX5005]                 SST34HF3282@FBGA62 [CX5005]  
SST34HF3283@FBGA56 [CX5005]                 SST34HF3283@FBGA62 [CX5005]  
SST34HF3284@FBGA56 [CX5005]                 SST34HF3284@FBGA62 [CX5005]  
SST34HF32A4@FBGA56 [CX5005]                 SST34HF32A4@FBGA62 [CX5005]  
SST34WA1601@FBGA44 [CX5099]                 SST34WA1602@FBGA44 [CX5099]  
SST36VF1601(B3K)@TFBGA48 [CX5002]           SST36VF1601@TSOP48 [CX1004]  
SST36VF1601(BK)@TFBGA48 [CX5005]           SST36VF1601C@TSOP48 [CX1004]  
SST36VF1601C@FBGA48 [CX5002]                SST36VF1601E@TSOP48 [CX1004]  
SST36VF1601E@FBGA48 [CX5002]                SST36VF1601G@TSOP48 [CX1004]  
SST36VF1601G@FBGA48 [CX5002]                SST36VF1601G@TSOP48 [CX1004]  
SST36VF1602(B3K)@TFBGA48 [CX5002]           SST36VF1602@TSOP48 [CX1004]  
SST36VF1602(BK)@TFBGA48 [CX5005]           SST36VF1602C@TSOP48 [CX1004]  
SST36VF1602C@FBGA48 [CX5002]                SST36VF1602E@TSOP48 [CX1004]  
SST36VF1602E@FBGA48 [CX5002]                SST36VF1602G@TSOP48 [CX1004]  
SST36VF1602G@FBGA48 [CX5002]                SST36VF3203@TSOP48 [CX1004]  
SST36VF3203@FBGA48 [CX5002]                 SST36VF3204@TSOP48 [CX1004]  
SST36VF3204@FBGA48 [CX5002]                 SST36VF3204@TSOP48 [CX1004]  
SST37VF010 [CX0001]                         SST37VF010@PLCC32 [CX2032]  
SST37VF010@VSOP32 [CX1003]                 SST37VF020 [CX0001]  
SST37VF020@PLCC32 [CX2032]                 SST37VF020@VSOP32 [CX1003]  
SST37VF040 [CX0001]                         SST37VF040@PLCC32 [CX2032]  
SST37VF040@VSOP32 [CX1003]                 SST37VF512 [CX0001]  
SST37VF512@PLCC32 [CX2032]                 SST37VF512@VSOP32 [CX1003]  
SST38UF166@TSOP48 [CX1004]                 SST38VF166@TSOP48 [CX1004]  
SST38VF6401@FBGA48 [CX5002]                 SST38VF6401@TSOP48 [CX1004]  
SST38VF6402@FBGA48 [CX5002]                 SST38VF6402@TSOP48 [CX1004]  
SST38VF6403@FBGA48 [CX5002]                 SST38VF6403@TSOP48 [CX1004]

SST38VF6404@FBGA48 [CX5002]                   SST38VF6404@TSOP48 [CX1004]  
SST39LF010@PLCC32 [CX2032]                   SST39LF010@TFBGA48 [CX5002]  
SST39LF010@VSOP32 [CX1003]                   SST39LF010@WFBGA34 [CX5037]  
SST39LF016@FBGA48 [CX5002]                   SST39LF016@TSOP40 [CX1006]  
SST39LF020@PLCC32 [CX2032]                   SST39LF020@TFBGA48 [CX5002]  
SST39LF020@VSOP32 [CX1003]                   SST39LF020@WFBGA34 [CX5037]  
SST39LF040@PLCC32 [CX2032]                   SST39LF040@TFBGA48 [CX5002]  
SST39LF040@VSOP32 [CX1003]                   SST39LF080@FBGA48 [CX5002]  
SST39LF080@TSOP40 [CX1006]                   SST39LF080Q@TSOP40 [CX1006]  
SST39LF100@FBGA48 [CX5002]                   SST39LF100@VSOP40 [CX1005]  
SST39LF160(B2)@TFBGA48 [CX5002]             SST39LF160@TFBGA48 [CX5005]  
SST39LF160@TSOP48 [CX1004]                   SST39LF200@TFBGA48 [CX5005]  
SST39LF200@TSOP48 [CX1043]  
SST39LF200A(B2/B3)@TFBGA48 [CX5002]  
SST39LF200A@TFBGA48 [CX5005]                SST39LF200A@TSOP48 [CX1043]  
SST39LF200A@WFBGA48 [CX5037]               SST39LF400@TFBGA48 [CX5005]  
SST39LF400@TSOP48 [CX1043]  
SST39LF400A(B2/B3)@TFBGA48 [CX5002]  
SST39LF400A@TFBGA48 [CX5005]                SST39LF400A@TSOP48 [CX1043]  
SST39LF400A@WFBGA48 [CX5037]               SST39LF512@PLCC32 [CX2032]  
SST39LF512@VSOP32 [CX1003]                   SST39LF800@TFBGA48 [CX5005]  
SST39LF800@TSOP48 [CX1004]  
SST39LF800A(B2/B3)@TFBGA48 [CX5002]  
SST39LF800A@TFBGA48 [CX5005]                SST39LF800A@TSOP48 [CX1004]  
SST39LF800A@WFBGA48 [CX5037]               SST39LF801C@TFBGA48 [CX5002]  
SST39LF801C@TSOP48 [CX1004]                   SST39LF801C@WFBGA48 [CX5038]  
SST39LF802C@TFBGA48 [CX5002]                SST39LF802C@TSOP48 [CX1004]  
SST39LF802C@WFBGA48 [CX5038]  
SST39LH010@PLCC32 [CX2032]                   SST39LH010@TSOP32 [CX1002]  
SST39LH040 [CX0001]                           SST39LH040@PLCC32 [CX2032]  
SST39LH040@TSOP32 [CX1002]                   SST39LH512 [CX0001]  
SST39LH512@PLCC32 [CX2032]                   SST39LH512@TSOP32 [CX1002]  
SST39SF010 [CX0001]                           SST39SF010@PLCC32 [CX2032]  
SST39SF010@VSOP32 [CX1003]                   SST39SF010A [CX0001]  
SST39SF010A@PLCC32 [CX2032]                  SST39SF010A@VSOP32 [CX1003]  
SST39SF020 [CX0001]                           SST39SF020@PLCC32 [CX2032]  
SST39SF020@VSOP32 [CX1003]                   SST39SF020A [CX0001]  
SST39SF020A@PLCC32 [CX2032]                  SST39SF020A@VSOP32 [CX1003]  
SST39SF020P [CX0001]                          SST39SF020P@PLCC32 [CX2032]  
SST39SF020P@VSOP32 [CX1003]                  SST39SF040 [CX0001]  
SST39SF040@PLCC32 [CX2032]                  SST39SF040@VSOP32 [CX1003]  
SST39SF040P [CX0001]                          SST39SF040P@PLCC32 [CX2032]  
SST39SF040P@VSOP32 [CX1003]                  SST39SF512 [CX0001]  
SST39SF512@PLCC32 [CX2032]                  SST39SF512@VSOP32 [CX1003]  
SST39SF512A [CX0001]                          SST39SF512A@PLCC32 [CX2032]  
SST39SF512A@VSOP32 [CX1003]                  SST39VF010 [CX0001]  
SST39VF010@PLCC32 [CX2032]                  SST39VF010@TFBGA48 [CX5002]  
SST39VF010@VSOP32 [CX1003]                  SST39VF016@FBGA48 [CX5002]  
SST39VF016@TSOP40 [CX1006]                  SST39VF016Q@TSOP40 [CX1006]  
SST39VF020 [CX0001]                          SST39VF020@PLCC32 [CX2032]  
SST39VF020@TFBGA48 [CX5002]                  SST39VF020@VSOP32 [CX1003]  
SST39VF020P [CX0001]                          SST39VF020P@PLCC32 [CX2032]  
SST39VF020P@VSOP32 [CX1003]                  SST39VF040 [CX0001]  
SST39VF040@PLCC32 [CX2032]                  SST39VF040@TFBGA48 [CX5002]  
SST39VF040@VSOP32 [CX1003]                  SST39VF040P [CX0001]  
SST39VF040P@PLCC32 [CX2032]                  SST39VF040P@VSOP32 [CX1003]  
SST39VF080@FBGA48 [CX5002]                  SST39VF080@TSOP40 [CX1006]  
SST39VF080Q@TSOP40 [CX1006]                  SST39VF088@TSOP48 [CX1004]  
SST39VF100@FBGA48 [CX5002]                  SST39VF100@VSOP40 [CX1005]

SST39VF160(B2)@TFBGA48 [CX5002]      SST39VF160@TFBGA48 [CX5005]  
SST39VF160@TSOP48 [CX1004]      SST39VF160@TSOP48(SLOW) [CX1043]  
SST39VF1601@TFBGA48 [CX5002]      SST39VF1601@TSOP48 [CX1004]  
SST39VF1601C@FBGA48 [CX5002]      SST39VF1601C@TSOP48 [CX1004]  
SST39VF1602@TFBGA48 [CX5002]      SST39VF1602@TSOP48 [CX1004]  
SST39VF1602C@FBGA48 [CX5002]      SST39VF1602C@TSOP48 [CX1004]  
SST39VF160Q@TSOP48 [CX1004]      SST39VF1681@TFBGA48 [CX5002]  
SST39VF1681@TSOP48 [CX1004]      SST39VF1682@TFBGA48 [CX5002]  
SST39VF1682@TSOP48 [CX1004]  
SST39VF200A(B2/B3)@TFBGA48 [CX5002]  
SST39VF200A@TFBGA48 [CX5005]      SST39VF200A@TSOP48 [CX1043]  
SST39VF200A@WFBGA48 [CX5037]      SST39VF320@TFBGA48 [CX5002]  
SST39VF320@TSOP48 [CX1004]      SST39VF3201@TFBGA48 [CX5002]  
SST39VF3201@TSOP48 [CX1004]      SST39VF3201B@FBGA48 [CX5002]  
SST39VF3201B@TSOP48 [CX1004]      SST39VF3201C@FBGA48 [CX5002]  
SST39VF3201C@TSOP48 [CX1004]      SST39VF3202@TFBGA48 [CX5002]  
SST39VF3202@TSOP48 [CX1004]      SST39VF3202B@FBGA48 [CX5002]  
SST39VF3202B@TSOP48 [CX1004]      SST39VF3202C@FBGA48 [CX5002]  
SST39VF3202C@TSOP48 [CX1004]      SST39VF400@TSOP48 [CX1043]  
SST39VF400A(B2/B3)@TFBGA48 [CX5002]  
SST39VF400A@TFBGA48 [CX5005]      SST39VF400A@TSOP48 [CX1043]  
SST39VF400A@WFBGA48 [CX5037]      SST39VF400Q@TSOP48 [CX1043]  
SST39VF512 [CX0001]      SST39VF512@PLCC32 [CX2032]  
SST39VF512@VSOP32 [CX1003]      SST39VF6401@TFBGA48 [CX5005]  
SST39VF6401@TSOP48 [CX1004]      SST39VF6401B@FBGA48 [CX5005]  
SST39VF6401B@TSOP48 [CX1004]      SST39VF6402@TFBGA48 [CX5005]  
SST39VF6402@TSOP48 [CX1004]      SST39VF6402B@FBGA48 [CX5005]  
SST39VF6402B@TSOP48 [CX1004]      SST39VF800@TSOP48 [CX1004]  
SST39VF800A(B2/B3)@TFBGA48 [CX5002]  
SST39VF800A@TFBGA48 [CX5005]      SST39VF800A@TSOP48 [CX1004]  
SST39VF800A@WFBGA48 [CX5037]      SST39VF800Q@TSOP48 [CX1004]  
SST39VF801C@TFBGA48 [CX5002]      SST39VF801C@TSOP48 [CX1004]  
SST39VF801C@WFBGA48 [CX5038]      SST39VF802C@TFBGA48 [CX5002]  
SST39VF802C@TSOP48 [CX1004]      SST39VF802C@WFBGA48 [CX5038]  
SST39WF1601D@FBGA48 [CX5002]      SST39WF1601D@WFBGA48 [CX5038]  
SST39WF1602D@FBGA48 [CX5002]      SST39WF1602D@WFBGA48 [CX5038]  
SST39WF400A(02)@TFBGA48 [CX5002]      SST39WF400A(02)@WFBGA48 [CX5037]  
SST39WF400A(03)@TFBGA48 [CX5002]      SST39WF400A(03)@WFBGA48 [CX5037]  
SST39WF400B(M2)@WFBGA48 [CX5038]      SST39WF400B(Y1)@WFBGA48 [CX5038]  
SST39WF400B@TFBGA48 [CX5002]      SST39WF800A(M2)@WFBGA48 [CX5038]  
SST39WF800A(Y1)@WFBGA48 [CX5037]      SST39WF800A@TFBGA48 [CX5002]  
SST39WF800B(M2)@WFBGA48 [CX5038]      SST39WF800B(Y1)@WFBGA48 [CX5037]  
SST39WF800B@TFBGA48 [CX5002]      SST49LF002@PLCC32 [CX2032]  
SST49LF002@VSOP32 [CX1003]      SST49LF002A@PLCC32 [CX2032]  
SST49LF002A@VSOP32 [CX1003]      SST49LF002B@PLCC32 [CX2032]  
SST49LF003A@PLCC32 [CX2032]      SST49LF003A@VSOP32 [CX1003]  
SST49LF003B@PLCC32 [CX2032]      SST49LF004@PLCC32 [CX2032]  
SST49LF004@VSOP32 [CX1003]      SST49LF004A@PLCC32 [CX2032]  
SST49LF004A@VSOP32 [CX1003]      SST49LF004B@PLCC32 [CX2032]  
SST49LF004B@VSOP32 [CX1003]      SST49LF004B@VSOP40 [CX1006]  
SST49LF008@PLCC32 [CX2032]      SST49LF008@VSOP32 [CX1003]  
SST49LF008A@PLCC32 [CX2032]      SST49LF008A@TSOP40 [CX1006]  
SST49LF008A@VSOP32 [CX1003]      SST49LF020@PLCC32 [CX2032]  
SST49LF020@VSOP32 [CX1003]      SST49LF020A@PLCC32 [CX2032]  
SST49LF020A@VSOP32 [CX1003]      SST49LF030A@PLCC32 [CX2032]  
SST49LF030A@VSOP32 [CX1003]      SST49LF040@PLCC32 [CX2032]  
SST49LF040@VSOP32 [CX1003]      SST49LF040A@PLCC32 [CX2032]  
SST49LF040A@VSOP32 [CX1003]      SST49LF040B@PLCC32 [CX2032]  
SST49LF040B@TSOP40 [CX1006]      SST49LF040B@VSOP32 [CX1003]

SST49LF080A@PLCC32 [CX2032]

SST49LF080A@VSOP32 [CX1003]

## MICROCONTROLLER

SST65P542R@SOIC28 [CX1033]  
SST89C54@PLCC44 [CX2044]  
SST89C58 [CX0001]  
SST89C58@TQFP44 [CX3003]  
SST89C58RC@QFN40 [CX4017]  
SST89E516RD [CX0001]  
SST89E516RD@TQFP44 [CX3003]  
SST89E516RD2@PLCC44 [CX2044]  
SST89E52RC [CX0001]  
SST89E52RC@TQFP44 [CX3003]  
SST89E52RD@PLCC44 [CX2044]  
SST89E52RD2 [CX0001]  
SST89E52RD2@TQFP44 [CX3003]  
SST89E54RC@PLCC44 [CX2044]  
SST89E54RD [CX0001]  
SST89E54RD@TQFP44 [CX3003]  
SST89E54RD2@PLCC44 [CX2044]  
SST89E54RD2A [CX0001]  
SST89E54RD2A@TQFP44 [CX3003]  
SST89E54RDA@PLCC44 [CX2044]  
SST89E554RC [CX0001]  
SST89E554RC@TQFP44 [CX3003]  
SST89E564@PLCC44 [CX2044]  
SST89E564RD [CX0001]  
SST89E564RD@TQFP44 [CX3003]  
SST89E58RD@PLCC44 [CX2044]  
SST89E58RD2 [CX0001]  
SST89E58RD2@TQFP44 [CX3003]  
SST89E58RD2A@PLCC44 [CX2044]  
SST89E58RDA [CX0001]  
SST89E58RDA@TQFP44 [CX3003]  
SST89V516RD@PLCC44 [CX2044]  
SST89V516RD2 [CX0001]  
SST89V516RD2@TQFP44 [CX3003]  
SST89V52RD@PLCC44 [CX2044]  
SST89V52RD2 [CX0001]  
SST89V52RD2@TQFP44 [CX3003]  
SST89V54RD2@PLCC44 [CX2044]  
SST89V54RC [CX0001]  
SST89V54RC@TQFP44 [CX3003]  
SST89V564@PLCC44 [CX2044]  
SST89V564RD [CX0001]  
SST89V564RD@TQFP44 [CX3003]  
SST89V58RD2@PLCC44 [CX2044]

SST89C54 [CX0001]  
SST89C54@TQFP44 [CX3003]  
SST89C58@PLCC44 [CX2044]  
SST89C58RC@PLCC44 [CX2044]  
SST89C58RC@TQFP44 [CX3003]  
SST89E516RD@PLCC44 [CX2044]  
SST89E516RD2 [CX0001]  
SST89E516RD2@TQFP44 [CX3003]  
SST89E52RC@PLCC44 [CX2044]  
SST89E52RD [CX0001]  
SST89E52RD@TQFP44 [CX3003]  
SST89E52RD2@PLCC44 [CX2044]  
SST89E54RC [CX0001]  
SST89E54RC@TQFP44 [CX3003]  
SST89E54RD@PLCC44 [CX2044]  
SST89E54RD2 [CX0001]  
SST89E54RD2@TQFP44 [CX3003]  
SST89E54RD2A@PLCC44 [CX2044]  
SST89E54RDA [CX0001]  
SST89E54RDA@TQFP44 [CX3003]  
SST89E554RC@PLCC44 [CX2044]  
SST89E564 [CX0001]  
SST89E564@TQFP44 [CX3003]  
SST89E564RD@PLCC44 [CX2044]  
SST89E58RD [CX0001]  
SST89E58RD@TQFP44 [CX3003]  
SST89E58RD2@PLCC44 [CX2044]  
SST89E58RD2A [CX0001]  
SST89E58RD2A@TQFP44 [CX3003]  
SST89E58RDA@PLCC44 [CX2044]  
SST89V516RD [CX0001]  
SST89V516RD@TQFP44 [CX3003]  
SST89V516RD2@PLCC44 [CX2044]  
SST89V52RD [CX0001]  
SST89V52RD@TQFP44 [CX3003]  
SST89V52RD2@PLCC44 [CX2044]  
SST89V54RD2 [CX0001]  
SST89V54RD2@TQFP44 [CX3003]  
SST89V54RC@PLCC44 [CX2044]  
SST89V564 [CX0001]  
SST89V564@TQFP44 [CX3003]  
SST89V564RD@PLCC44 [CX2044]  
SST89V58RD2 [CX0001]  
SST89V58RD2@TQFP44 [CX3003]

## SST-CUSTOMER

### E (E) PROM/FRAM/NVRAM

SST39SF010A@PLCC32 [CX2032]

SST39SF020A@PLCC32 [CX2032]

## SSU

## MICROCONTROLLER

SSU2C508 [CX0001]  
SSU6C676 [CX0001]  
SSU6C676@TSSOP14 [CX1000]  
SSU6C74 [CX0001]

SSU2C508N [CX0001]  
SSU6C676@SOIC14 [CX1030]  
SSU6C73 [CX0001]

## ST

### E (E) PROM/FRAM/NVRAM

ET2716 [CX0001]  
ETC2732 [CX0001]  
M13C02@SOIC8 [CX1045]  
M24128@MLP8 [CX4002]  
M24128@TSOP8 [CX1059]  
M24164@SOIC8 [CX1045]  
M24256@MLP8 [CX4002]  
M24256@SOIC8[5.5] [CX1044]  
M24256BF@MLP8 [CX4002]  
M24256BF@SOIC8[5.5] [CX1044]  
M24256BR [CX0001]  
M24256BR@SOIC8[3.9] [CX1045]  
M24256BR@TSOP8 [CX1059]  
M24256BW@MLP8 [CX4002]  
M24256BW@SOIC8[5.5] [CX1044]  
M24512 [CX0001]  
M24512@SOIC8(208 mil) [CX1044]  
M24C01 [CX0001]  
M24C01@SOIC8 [CX1045]  
M24C01R@MLP8 [CX4002]  
M24C01R@TSOP8 [CX1059]  
M24C01W@MLP8 [CX4002]  
M24C01W@TSOP8 [CX1059]  
M24C02@MLP8 [CX4002]  
M24C02R [CX0001]  
M24C02R@SOIC8 [CX1045]  
M24C02W [CX0001]  
M24C02W@SOIC8 [CX1045]  
M24C04 [CX0001]  
M24C04@SOIC8 [CX1045]  
M24C04R@MLP8 [CX4002]  
M24C04R@TSOP8 [CX1059]  
M24C04W@MLP8 [CX4002]  
M24C04W@TSOP8 [CX1059]  
M24C08@MLP8 [CX4002]  
M24C08@SOIC8 [CX1045]  
M24C08R [CX0001]  
M24C08R@MSOP8 [CX4007]  
M24C08R@TSOP8 [CX1059]  
M24C08W@MLP8 [CX4002]  
M24C08W@SOIC8 [CX1045]  
M24C128(BN) [CX0001]  
M24C128(MW)@SOIC8 [CX1045]  
M24C128B(BN) [CX0001]  
M24C128B(MW)@SOIC8 [CX1045]  
M24C16 [CX0001]

ETC2716 [CX0001]  
M13C02 [CX0001]  
M24128 [CX0001]  
M24128@SOIC8 [CX1045]  
M24164 [CX0001]  
M24256 [CX0001]  
M24256@SOIC8[3.9] [CX1045]  
M24256@TSOP8 [CX1059]  
M24256BF@SOIC8[3.9] [CX1045]  
M24256BF@TSOP8 [CX1059]  
M24256BR@MLP8 [CX4002]  
M24256BR@SOIC8[5.5] [CX1044]  
M24256BW [CX0001]  
M24256BW@SOIC8[3.9] [CX1045]  
M24256BW@TSOP8 [CX1059]  
M24512@SOIC8(150 mil) [CX1045]  
M24512@TSOP8 [CX1059]  
M24C01@MLP8 [CX4002]  
M24C01R [CX0001]  
M24C01R@SOIC8 [CX1045]  
M24C01W [CX0001]  
M24C01W@SOIC8 [CX1045]  
M24C02 [CX0001]  
M24C02@SOIC8 [CX1045]  
M24C02R@MLP8 [CX4002]  
M24C02R@TSOP8 [CX1059]  
M24C02W@MLP8 [CX4002]  
M24C02W@TSOP8 [CX1059]  
M24C04@MLP8 [CX4002]  
M24C04R [CX0001]  
M24C04R@SOIC8 [CX1045]  
M24C04W [CX0001]  
M24C04W@SOIC8 [CX1045]  
M24C08 [CX0001]  
M24C08@MSOP8 [CX4007]  
M24C08@TSOP8 [CX1059]  
M24C08R@MLP8 [CX4002]  
M24C08R@SOIC8 [CX1045]  
M24C08W [CX0001]  
M24C08W@MSOP8 [CX4007]  
M24C08W@TSOP8 [CX1059]  
M24C128(MN)@SOIC8 [CX1044]  
M24C128@MLP8 [CX4002]  
M24C128B(MN)@SOIC8 [CX1044]  
M24C128B@MLP8 [CX4002]  
M24C16@MLP8 [CX4002]

M24C16@SOIC8 [CX1045]  
M24C16R@MLP8 [CX4002]  
M24C16R@TSOP8 [CX1059]  
M24C16W@MLP8 [CX4002]  
M24C16W@TSOP8 [CX1059]  
M24C256(MN)@SOIC8 [CX1044]  
M24C256@MLP8 [CX4002]  
M24C256A(MN)@SOIC8 [CX1044]  
M24C256A@MLP8 [CX4002]  
M24C256B(MN)@SOIC8 [CX1044]  
M24C256B@MLP8 [CX4002]  
M24C256W(MN)@SOIC8 [CX1044]  
M24C256W@MLP8 [CX4002]  
M24C32(DL)@TSSOP14 [CX1000]  
M24C32(MN)@SOIC8 [CX1044]  
M24C32@MLP8 [CX4002]  
M24C32W(DL)@TSSOP14 [CX1000]  
M24C32W(MN)@SOIC8 [CX1045]  
M24C32W@MLP8 [CX4002]  
M24C64(DL)@TSSOP14 [CX1000]  
M24C64(MN)@SOIC8 [CX1044]  
M24C64@MLP8 [CX4002]  
M24C64W(DL)@TSSOP14 [CX1000]  
M24C64W(MN)@SOIC8 [CX1044]  
M24C64W@MLP8 [CX4002]  
M24CL04B@MLP8 [CX4002]  
M24CL04B@TSOP8 [CX1059]  
M24E32(BN) [CX0001]  
M24E32(MN)@SOIC8 [CX1044]  
M24M01@LGA8 [CX4006]  
M24M01-HR@SOIC8(150 mil) [CX1045]  
M24M01-HR@SOIC8(200 mil) [CX1044]  
M24M01-HR@WLCSP8 [CX0001]  
M24M01-R@SOIC8(200 mil) [CX1044]  
M24M01-W@SOIC8(150 mil) [CX1045]  
M24M01-W@WLCSP8 [CX0001]  
M24W01@SOIC8 [CX1045]  
M24W02@SOIC8 [CX1045]  
M24W04@SOIC8 [CX1045]  
M24W08@SOIC8 [CX1045]  
M24W16@SOIC8 [CX1045]  
M25C02 [CX0001]  
M25C08 [CX0001]  
M25E16 [CX0001]  
M25P05@VQFPN8 [CX4005]  
M25P05-A@TSSOP8 [CX1059#3]  
M25P10@SOIC8 [CX1045]  
M25P10@VQFPN8 [CX4005]  
M25P10-A@VFQFPN8 [CX4005#1]  
M25P128@SOIC16(ISP) [CX0001]  
M25P128@VDFPN8(ISP) [CX0001]  
M25P16@SOIC16(ISP) [CX0001]  
M25P16@SOIC8(150mil)(ISP) [CX0001]  
M25P16@SOIC8(200mil) [CX1044#1]  
M25P16@SOIC8(200mil)(ISP) [CX0001]  
M25P16@VDFPN8 [CX4006#1]  
M25P16@VFQFPN8 [CX4005#1]  
M25P20@SOIC8 [CX1045#1]  
M25P32(Fast Mode)@SOIC16 [CX1033#1]  
M24C16R [CX0001]  
M24C16R@SOIC8 [CX1045]  
M24C16W [CX0001]  
M24C16W@SOIC8 [CX1045]  
M24C256(BN) [CX0001]  
M24C256(MW)@SOIC8 [CX1045]  
M24C256A(BN) [CX0001]  
M24C256A(MW)@SOIC8 [CX1045]  
M24C256B(BN) [CX0001]  
M24C256B(MW)@SOIC8 [CX1045]  
M24C256W(BN) [CX0001]  
M24C256W(MW)@SOIC8 [CX1045]  
M24C32(BN) [CX0001]  
M24C32(DW)@TSSOP8 [CX1059]  
M24C32(MW)@SOIC8 [CX1045]  
M24C32W(BN) [CX0001]  
M24C32W(DW)@TSSOP8 [CX1059]  
M24C32W(MW)@SOIC8 [CX1044]  
M24C64(BN) [CX0001]  
M24C64(DW)@TSSOP8 [CX1059]  
M24C64(MW)@SOIC8 [CX1045]  
M24C64W(BN) [CX0001]  
M24C64W(DW)@TSSOP8 [CX1059]  
M24C64W(MW)@SOIC8 [CX1045]  
M24CL04B [CX0001]  
M24CL04B@SOIC8 [CX1045]  
M24E16 [CX0001]  
M24E32(DW)@TSSOP8 [CX1059]  
M24E32(MW)@SOIC8 [CX1045]  
M24M01@SOIC8 [CX1045]  
M24M01-R@SOIC8(150 mil) [CX1045]  
M24M01-R@WLCSP8 [CX0001]  
M24M01-W@SOIC8(200 mil) [CX1044]  
M24W01 [CX0001]  
M24W02 [CX0001]  
M24W04 [CX0001]  
M24W08 [CX0001]  
M24W16 [CX0001]  
M25C01 [CX0001]  
M25C04 [CX0001]  
M25C16 [CX0001]  
M25P05@SOIC8 [CX1045]  
M25P05-A@SOIC8 [CX1045#1]  
M25P05-A@VDFPN8 [CX4005#1]  
M25P10@UFDFPN8 [CX4002]  
M25P10-A@SOIC8 [CX1045#1]  
M25P128@SOIC16 [CX1033#1]  
M25P128@VDFPN8 [CX4006#1]  
M25P16@SOIC16 [CX1033#1]  
M25P16@SOIC8(150mil) [CX1045#1]  
M25P16@VDFPN8(ISP) [CX0001]  
M25P16@VFQFPN8(ISP) [CX0001]  
M25P20@VFQFPN8 [CX4005#1]

M25P32(Fast Mode)@SOIC8(150mil) [CX1044#1]  
M25P32(Fast Mode)@SOIC8(200mil) [CX4005#1]  
M25P32(Fast Mode)@VQFPN8 [CX4006#1]  
M25P32@SOIC16 [CX1033#1] M25P32@SOIC16(ISP) [CX0001]  
M25P32@SOIC8 [CX1044#1] M25P32@SOIC8(ISP) [CX0001]  
M25P32@VDFPN8 [CX4006#1] M25P32@VDFPN8(ISP) [CX0001]  
M25P32@VFQFPN8 [CX4005#1] M25P32@VFQFPN8(ISP) [CX0001]  
M25P40@SOIC8 [CX1045#1] M25P40@VFQFPN8 [CX4005#1]  
M25P64(Fast Mode)@SOIC16 [CX1033#1]  
M25P64(Fast Mode)@VDFPN8 [CX4006#1]  
M25P64@SOIC16 [CX1033#1] M25P64@SOIC16(ISP) [CX0001]  
M25P64@VDFPN8 [CX4006#1] M25P64@VDFPN8(ISP) [CX0001]  
M25P80@SOIC16 [CX1033#1] M25P80@SOIC8 [CX1044#1]  
M25P80@VFQFPN8 [CX4005#1] M25PE10@SOIC8 [CX1045#1]  
M25PE10@SOIC8(ISP) [CX0001] M25PE10@VQFPN8 [CX4005#1]  
M25PE10@VQFPN8(ISP) [CX0001] M25PE16@SOIC8 [CX1044#1]  
M25PE16@VQFPN8 [CX4005#1] M25PE20@SOIC8 [CX1045#1]  
M25PE20@SOIC8(ISP) [CX0001] M25PE20@VQFPN8 [CX4005#1]  
M25PE20@VQFPN8(ISP) [CX0001] M25PE40@SOIC8 [CX1044#1]  
M25PE40@SOIC8(ISP) [CX0001] M25PE40@VQFPN8 [CX4005#1]  
M25PE40@VQFPN8(ISP) [CX0001] M25PE80@SOIC8 [CX1044#1]  
M25PE80@SOIC8(ISP) [CX0001] M25PE80@VQFPN8 [CX4005#1]  
M25PE80@VQFPN8(ISP) [CX0001] M25PX32@SOIC16 [CX1033#1]  
M25PX32@SOIC8 [CX1044#1] M25PX32@TBGA24 [CX5157]  
M25PX32@VFQFPN8 [CX4005#1] M25PX64@SOIC16 [CX1033#1]  
M25PX64@TBGA24 [CX5157]  
M25PX64@TBGA24(SKYWORTH) [CX5157]  
M25PX64@VDFPN8 [CX4006#1] M25W01 [CX0001]  
M25W02 [CX0001] M25W04 [CX0001]  
M25W08 [CX0001] M25W16 [CX0001]  
M25W166 [CX0001] M27128A [CX0001]  
M2716 [CX0001] M2716F1 [CX0001]  
M27256 [CX0001] M27256A [CX0001]  
M2732A [CX0001] M27512 [CX0001]  
M2764 [CX0001] M2764A [CX0001]  
M27C1000 [CX0001] M27C1000@PLCC32 [CX2032]  
M27C1000@TSOP32 [CX1002] M27C1001 [CX0001]  
M27C1001@PLCC32 [CX2032] M27C1001@TSOP32 [CX1002]  
M27C1024 [CX0001] M27C1024@PLCC44 [CX2044]  
M27C128B [CX0001] M27C16 [CX0001]  
M27C160 [CX0001] M27C160@PLCC44 [CX2044]  
M27C160@PSOP44 [CX1014] M27C160K [CX0001]  
M27C160K@PLCC44 [CX2044] M27C160K@PSOP44 [CX1014]  
M27C2001 [CX0001] M27C2001@PLCC32 [CX2032]  
M27C2001@TSOP32 [CX1002] M27C202 [CX0001]  
M27C202@PLCC44 [CX2044] M27C202@VSOP40 [CX1005]  
M27C256B [CX0001] M27C256B@PLCC32 [CX2032]  
M27C32 [CX0001] M27C322 [CX0001]  
M27C322@SDIP42 [CX0042] M27C400 [CX0001]  
M27C4001 [CX0001] M27C4001@PLCC32 [CX2032]  
M27C4001@TSOP32 [CX1002] M27C4002 [CX0001]  
M27C4002@PLCC44 [CX2044] M27C405 [CX0001]  
M27C405@PLCC32 [CX2032] M27C405@TSOP32 [CX1002]  
M27C512 [CX0001] M27C512@PLCC32 [CX2032]  
M27C513 [CX0001] M27C516 [CX0001]  
M27C516@PLCC44 [CX2044] M27C64A [CX0001]  
M27C64A@PLCC32 [CX2032] M27C800 [CX0001]  
M27C800@PLCC44 [CX2044] M27C800@PSOP44 [CX1014]  
M27C801 [CX0001] M27C801@PLCC32 [CX2032]



M27C801@TSOP32 [CX1002]  
M27HC641@PLCC28 [CX2028]  
M27HC642@PLCC28 [CX2028]  
M27V101@PLCC32 [CX2032]  
M27V102 [CX0001]  
M27V160 [CX0001]  
M27V160@PSOP44 [CX1014]  
M27V160K@PLCC44 [CX2044]  
M27V201 [CX0001]  
M27V201@TSOP32 [CX1002]  
M27V322 [CX0001]  
M27V401 [CX0001]  
M27V401@TSOP32 [CX1002]  
M27V402@PLCC44 [CX2044]  
M27V405 [CX0001]  
M27V405@TSOP32 [CX1002]  
M27V512@PLCC32 [CX2032]  
M27V800 [CX0001]  
M27V801 [CX0001]  
M27V801@TSOP32 [CX1002]  
M27W016@PSOP44 [CX1014]  
M27W016@TSOP48 [CX1004]  
M27W032@TSOP48 [CX1004]  
M27W064@TSOP48 [CX1004]  
M27W101@PLCC32 [CX2032]  
M27W102 [CX0001]  
M27W160 [CX0001]  
M27W160@PSOP44 [CX1014]  
M27W201@PLCC32 [CX2032]  
M27W202 [CX0001]  
M27W202@VSOP40 [CX1005]  
M27W400@PLCC44 [CX2044]  
M27W401@PLCC32 [CX2032]  
M27W402 [CX0001]  
M27W402@TSOP40 [CX1006]  
M27W512@PLCC32 [CX2032]  
M27W800 [CX0001]  
M27W801 [CX0001]  
M27W801@TSOP32 [CX1002]  
M28010@PLCC32 [CX2032]  
M28010R [CX0001]  
M28010R@TSOP32 [CX1002]  
M28010W@PLCC32 [CX2032]  
M28256 [CX0001]  
M28256@TSOP28 [CX1024]  
M28C010@PLCC32 [CX2032]  
M28C010R [CX0001]  
M28C010R@TSOP32 [CX1002]  
M28C010W@PLCC32 [CX2032]  
M28C16@PLCC32 [CX2032]  
M28C64 [CX0001]  
M28C64@TSOP28 [CX1024]  
M28C64C@PLCC32 [CX2032]  
M28C64C@TSOP28 [CX1024]  
M28C64X@PLCC32 [CX2032]  
M28F101 [CX0001]  
M28F101@PLCC32 [CX2032]  
M28F102 [CX0001]  
M28F102@TSOP40 [CX1005]  
M27HC641 [CX0001]  
M27HC642 [CX0001]  
M27V101 [CX0001]  
M27V101@TSOP32 [CX1002]  
M27V102@PLCC44 [CX2044]  
M27V160@PLCC44 [CX2044]  
M27V160K [CX0001]  
M27V160K@PSOP44 [CX1014]  
M27V201@PLCC32 [CX2032]  
M27V256 [CX0001]  
M27V322@SDIP42 [CX0042]  
M27V401@PLCC32 [CX2032]  
M27V402 [CX0001]  
M27V402@TSOP40 [CX1006]  
M27V405@PLCC32 [CX2032]  
M27V512 [CX0001]  
M27V512@TSOP28 [CX1024]  
M27V800@PLCC44 [CX2044]  
M27V801@PLCC32 [CX2032]  
M27W016 [CX0001]  
M27W016@SDIP42 [CX0042]  
M27W032@PSOP44 [CX1014]  
M27W064@PSOP44 [CX1014]  
M27W101 [CX0001]  
M27W101@TSOP32 [CX1002]  
M27W102@PLCC44 [CX2044]  
M27W160@PLCC44 [CX2044]  
M27W201 [CX0001]  
M27W201@TSOP32 [CX1002]  
M27W202@PLCC44 [CX2044]  
M27W400 [CX0001]  
M27W401 [CX0001]  
M27W401@TSOP32 [CX1002]  
M27W402@PLCC44 [CX2044]  
M27W512 [CX0001]  
M27W512@TSOP28 [CX1024]  
M27W800@PLCC44 [CX2044]  
M27W801@PLCC32 [CX2032]  
M28010 [CX0001]  
M28010@TSOP32 [CX1002]  
M28010R@PLCC32 [CX2032]  
M28010W [CX0001]  
M28010W@TSOP32 [CX1002]  
M28256@PLCC32 [CX2032]  
M28C010 [CX0001]  
M28C010@TSOP32 [CX1002]  
M28C010R@PLCC32 [CX2032]  
M28C010W [CX0001]  
M28C010W@TSOP32 [CX1002]  
M28C17@SOIC28 [CX1033]  
M28C64@PLCC32 [CX2032]  
M28C64C [CX0001]  
M28C64C@SOIC28 [CX1033]  
M28C64X [CX0001]  
M28C64X@TSOP28 [CX1024]  
M28F101(REVERSE)@TSOP32 [CX1002]  
M28F101@TSOP32 [CX1002]  
M28F102@PLCC44 [CX2044]  
M28F151 [CX0001]

M28F151(REVERSE)@TSOP32 [CX1002]	M28F151@PLCC32 [CX2032]
M28F151@TSOP32 [CX1002]	M28F201 [CX0001]
M28F201(REVERSE)@TSOP32 [CX1002]	M28F201@PLCC32 [CX2032]
M28F201@TSOP32 [CX1002]	M28F210@PSOP44 [CX1014]
M28F210@TSOP48 [CX1004]	M28F211@TSOP40 [CX1006]
M28F220@PSOP44 [CX1014]	M28F220@TSOP48 [CX1004]
M28F221@TSOP40 [CX1006]	M28F256 [CX0001]
M28F256(REVERSE)@TSOP32 [CX1002]	M28F256@PLCC32 [CX2032]
M28F256@TSOP32 [CX1002]	M28F411@TSOP40 [CX1006]
M28F421@TSOP40 [CX1006]	M28F512 [CX0001]
M28F512(REVERSE)@TSOP32 [CX1002]	M28F512@PLCC32 [CX2032]
M28F512@TSOP32 [CX1002]	M28LV64 [CX0001]
M28LV64@PLCC32 [CX2032]	M28LV64@TSOP28 [CX1024]
M28R400CB@FBGA48 [CX5031]	M28R400CT@FBGA48 [CX5031]
M28V411@TSOP40 [CX1006]	M28V421@TSOP40 [CX1006]
M28W160B@FBGA48 [CX5031]	M28W160B@TSOP48 [CX1004]
M28W160BB@FBGA48 [CX5031]	M28W160BB@TSOP48 [CX1004]
M28W160BT@FBGA48 [CX5031]	M28W160BT@TSOP48 [CX1004]
M28W160CB@FBGA48 [CX5031]	M28W160CB@TSOP48 [CX1004]
M28W160CT@FBGA48 [CX5031]	M28W160CT@TSOP48 [CX1004]
M28W160ECB@FBGA48 [CX5031]	M28W160ECB@TSOP48 [CX1004]
M28W160ECT@FBGA48 [CX5031]	M28W160ECT@TSOP48 [CX1004]
M28W160ESB@FBGA64 [CX5004]	M28W160EST@FBGA64 [CX5004]
M28W160FSB@FBGA46 [CX5031]	M28W160FSB@FBGA64 [CX5004]
M28W160FST@FBGA46 [CX5031]	M28W160FST@FBGA64 [CX5004]
M28W160T@FBGA48 [CX5031]	M28W160T@TSOP48 [CX1004]
M28W320CB@FBGA48 [CX5031]	M28W320CB@TSOP48 [CX1004]
M28W320CT@FBGA48 [CX5031]	M28W320CT@TSOP48 [CX1004]
M28W320ECB@FBGA48 [CX5031]	M28W320ECB@TSOP48 [CX1004]
M28W320ECT@FBGA48 [CX5031]	M28W320ECT@TSOP48 [CX1004]
M28W320FCB@FBGA48 [CX5031]	M28W320FCB@TSOP48 [CX1004]
M28W320FCT@FBGA48 [CX5031]	M28W320FCT@TSOP48 [CX1004]
M28W320FSB@FBGA47 [CX5031]	M28W320FSB@FBGA64 [CX5004]
M28W320FST@FBGA47 [CX5031]	M28W320FST@FBGA64 [CX5004]
M28W320FSU(Double)@FBGA64 [CX5004]	M28W320FSU@FBGA64 [CX5004]
M28W320FSU@FBGA47 [CX5031]	M28W320HSB@FBGA64 [CX5004]
M28W320HSB@FBGA47 [CX5031]	M28W320HST@FBGA64 [CX5004]
M28W320HST@FBGA47 [CX5031]	
M28W320HSU(Double)@FBGA64 [CX5004]	
M28W320HSU@FBGA64 [CX5004]	M28W640CB@FBGA48 [CX5078]
M28W640CB@TSOP48 [CX1004]	M28W640CT@FBGA48 [CX5078]
M28W640CT@TSOP48 [CX1004]	M28W640ECB@FBGA48 [CX5078]
M28W640ECB@TSOP48 [CX1004]	M28W640ECT@FBGA48 [CX5078]
M28W640ECT@TSOP48 [CX1004]	M28W640FCB@FBGA48 [CX5078]
M28W640FCB@TSOP48 [CX1004]	M28W640FCT@FBGA48 [CX5078]
M28W640FCT@TSOP48 [CX1004]	M28W640FSB@FBGA64 [CX5004]
M28W640FST@FBGA64 [CX5004]	M28W640FSU@FBGA64 [CX5004]
M28W640HCB@FBGA48 [CX5078]	M28W640HCB@TSOP48 [CX1004]
M28W640HCT@FBGA48 [CX5078]	M28W640HCT@TSOP48 [CX1004]
M28W640HSB@FBGA48 [CX5031]	M28W640HSB@FBGA64 [CX5004]
M28W640HST@FBGA48 [CX5031]	M28W640HST@FBGA64 [CX5004]
M28W640HSU@FBGA48 [CX5031]	M28W640HSU@FBGA64 [CX5004]
M28W800B@FBGA48 [CX5031]	M28W800B@TSOP48 [CX1004]
M28W800BB@FBGA48 [CX5031]	M28W800BB@TSOP48 [CX1004]
M28W800BT@FBGA48 [CX5031]	M28W800BT@TSOP48 [CX1004]
M28W800CB@FBGA48 [CX5031]	M28W800CB@TSOP48 [CX1004]
M28W800CT@FBGA48 [CX5031]	M28W800CT@TSOP48 [CX1004]
M28W800T@FBGA48 [CX5031]	M28W800T@TSOP48 [CX1004]
M29DW127G@FBGA64 [CX5004]	M29DW127G@TSOP56 [CX1011]

M29DW128F(Mirror)@FBGA64 [CX5004]  
M29DW128F(Mirror)@TSOP56 [CX1011]  
M29DW128F(Q\_Word)@FBGA64 [CX5004]  
M29DW128F(Q\_Word)@TSOP56 [CX1011]  
M29DW128G@FBGA64 [CX5004]  
M29DW256G@LFBGA64 [CX5074]  
M29DW256G@TSOP56 [CX1055]  
M29DW323DB@TFBGA63 [CX5047]  
M29DW323DT@TFBGA48 [CX5002]  
M29DW323DT@TSOP48 [CX1004]  
M29DW324DB@TFBGA63 [CX5047]  
M29DW324DT@TFBGA48 [CX5002]  
M29DW324DT@TSOP48 [CX1004]  
M29DW640F@FBGA48 [CX5002]  
M29DW641F@FBGA48 [CX5002]  
M29F002B [CX0001]  
M29F002B@TSOP32 [CX1002]  
M29F002BB@PLCC32 [CX2032]  
M29F002BNT [CX0001]  
M29F002BNT@TSOP32 [CX1002]  
M29F002BT@PLCC32 [CX2032]  
M29F002T [CX0001]  
M29F002T@TSOP32 [CX1002]  
M29F010B@PLCC32 [CX2032]  
M29F016B@PSOP44 [CX1014]  
M29F016D@PSOP44 [CX1014]  
M29F032D@TSOP40 [CX1006]  
M29F040@PLCC32 [CX2032]  
M29F040B [CX0001]  
M29F040B@TSOP32 [CX1002]  
M29F080A@TSOP40 [CX1006]  
M29F080D@TSOP40 [CX1006]  
M29F100B@TSOP48 [CX1004]  
M29F100T@TSOP48 [CX1004]  
M29F102B@TSOP40 [CX1005]  
M29F102BB@TSOP40 [CX1005]  
M29F160BT@TSOP48 [CX1004]  
M29F160FB@TSOP48 [CX1043]  
M29F160FT@TSOP48 [CX1043]  
M29F200B@TSOP48 [CX1004]  
M29F200BB@TSOP48 [CX1004]  
M29F200BT@TSOP48 [CX1004]  
M29F200FB@PSOP44 [CX1014]  
M29F200FT@FBGA48 [CX5002]  
M29F200FT@TSOP48 [CX1043]  
M29F200T@TSOP48 [CX1004]  
M29F400B@PSOP44 [CX1014]  
M29F400BB@PSOP44 [CX1014]  
M29F400BT@PSOP44 [CX1014]  
M29F400FB@FBGA48 [CX5002]  
M29F400FB@TSOP48 [CX1043]  
M29F400FT@PSOP44 [CX1014]  
M29F400T@PSOP44 [CX1014]  
M29F512B@PLCC32 [CX2032]  
M29F640MT@TSOP48 [CX1043]  
M29F800AB@TSOP48 [CX1004]  
M29F800AT@TSOP48 [CX1004]  
M29F800DB@TSOP48 [CX1004]  
M29F800DT@TSOP48 [CX1004]  
M29DW128G@TSOP56 [CX1055]  
M29DW256G@TFBGA64 [CX5004]  
M29DW323DB@TFBGA48 [CX5002]  
M29DW323DB@TSOP48 [CX1004]  
M29DW323DT@TFBGA63 [CX5047]  
M29DW324DB@TFBGA48 [CX5002]  
M29DW324DB@TSOP48 [CX1004]  
M29DW324DT@TFBGA63 [CX5047]  
M29DW640D@TSOP48 [CX1004]  
M29DW640F@TSOP48 [CX1004]  
M29DW641F@TSOP48 [CX1004]  
M29F002B@PLCC32 [CX2032]  
M29F002BB [CX0001]  
M29F002BB@TSOP32 [CX1002]  
M29F002BNT@PLCC32 [CX2032]  
M29F002BT [CX0001]  
M29F002BT@TSOP32 [CX1002]  
M29F002T@PLCC32 [CX2032]  
M29F010B [CX0001]  
M29F010B@TSOP32 [CX1002]  
M29F016B@TSOP40 [CX1006]  
M29F016D@TSOP40 [CX1006]  
M29F040 [CX0001]  
M29F040@TSOP32 [CX1002]  
M29F040B@PLCC32 [CX2032]  
M29F080A@PSOP44 [CX1014]  
M29F080D@PSOP44 [CX1014]  
M29F100B@PSOP44 [CX1014]  
M29F100T@PSOP44 [CX1014]  
M29F102B@PLCC44 [CX2044]  
M29F102BB@PLCC44 [CX2044]  
M29F160BB@TSOP48 [CX1004]  
M29F160FB@FBGA48 [CX5002]  
M29F160FT@FBGA48 [CX5002]  
M29F200B@PSOP44 [CX1014]  
M29F200BB@PSOP44 [CX1014]  
M29F200BT@PSOP44 [CX1014]  
M29F200FB@FBGA48 [CX5002]  
M29F200FB@TSOP48 [CX1043]  
M29F200FT@PSOP44 [CX1014]  
M29F200T@PSOP44 [CX1014]  
M29F320MT@TSOP48 [CX0001]  
M29F400B@TSOP48 [CX1004]  
M29F400BB@TSOP48 [CX1004]  
M29F400BT@TSOP48 [CX1004]  
M29F400FB@PSOP44 [CX1014]  
M29F400FT@FBGA48 [CX5002]  
M29F400FT@TSOP48 [CX1043]  
M29F400T@TSOP48 [CX1004]  
M29F512B@TSOP32 [CX1003]  
M29F800AB@PSOP44 [CX1014]  
M29F800AT@PSOP44 [CX1014]  
M29F800DB@PSOP44 [CX1014]  
M29F800DT@PSOP44 [CX1014]  
M29F800FB@FBGA48 [CX5002]

M29F800FB@PSOP44 [CX1014]  
M29F800FT@FBGA48 [CX5002]  
M29F800FT@TSOP48 [CX1043]  
M29KW016E@TFBGA48 [CX5002]  
M29KW032E@TFBGA48 [CX5002]  
M29KW064E@TFBGA48 [CX5002]  
M29PW032@BGA48 [CX5157]  
M29PW032@TSOP48 [CX0001]  
M29S256LP@FBGA88 [CX5005]  
M29V040@TSOP32 [CX1002]  
M29W004BB@TSOP40 [CX1006]  
M29W004T@TSOP40 [CX1006]  
M29W008AT@TSOP40 [CX1006]  
M29W008T@TSOP40 [CX1006]  
M29W010B@TSOP32 [CX1002]  
M29W017D@TSOP40 [CX1006]  
M29W022BB@PLCC32 [CX2032]  
M29W022BT [CX0001]  
M29W022BT@TSOP32 [CX1002]  
M29W040@TSOP32 [CX1002]  
M29W040B@TSOP32 [CX1002]  
M29W064FB@TSOP48 [CX1004]  
M29W064FT@TSOP48 [CX1004]  
M29W102BT@TSOP40 [CX1005]  
M29W116BT@TSOP40 [CX1006]  
M29W128FH(Mirror)@FBGA64 [CX5004]  
M29W128FH(Mirror)@TSOP56 [CX1011]  
M29W128FH(Q\_Word)@FBGA64 [CX5004]  
M29W128FH(Q\_Word)@TSOP56 [CX1011]  
M29W128FL(Mirror)@FBGA64 [CX5004]  
M29W128FL(Mirror)@TSOP56 [CX1011]  
M29W128FL(Q\_Word)@FBGA64 [CX5004]  
M29W128FL(Q\_Word)@TSOP56 [CX1011]  
M29W128GH(SD)@TSOP56 [CX1011]  
M29W128GH@TSOP56 [CX1011]  
M29W128GL@TSOP56 [CX1011]  
M29W128GSH@FBGA64(ZS) [CX5074]  
M29W128GSL@FBGA64 [CX5004]  
M29W128GSL@TSOP56 [CX1055]  
M29W160BB@PSOP44 [CX1014]  
M29W160BT@LBGA48 [CX5022]  
M29W160BT@TSOP48 [CX1004]  
M29W160DB@PSOP44 [CX1014]  
M29W160DT@LBGA48 [CX5022]  
M29W160DT@TSOP48 [CX1004]  
M29W160EB@LBGA64 [CX5074]  
M29W160EB@TSOP48 [CX1004]  
M29W160ET@LBGA64 [CX5074]  
M29W160ET@TSOP48 [CX1004]  
M29W160FB@TSOP48 [CX1004]  
M29W160FT@TSOP48 [CX1004]  
M29W200BB@TSOP48 [CX1004]  
M29W200BT@TSOP48 [CX1004]  
M29W256AD@FBGA88 [CX5005]  
M29W256ADP@FBGA88 [CX5005]  
M29W256G2G@TSOP56 [CX0051]  
M29W256GH@TFBGA64 [CX5004]  
M29W256GL@LFBGA64 [CX5074]  
M29W256GL@TSOP56 [CX1055]  
M29F800FB@TSOP48 [CX1043]  
M29F800FT@PSOP44 [CX1014]  
M29KW016E@PSOP44 [CX1014]  
M29KW016E@TSOP48 [CX1004]  
M29KW032E@TSOP48 [CX1004]  
M29KW064E@TSOP48 [CX1004]  
M29PW032@PSOP44 [CX0001]  
M29S128LP@FBGA88 [CX5005]  
M29V040@PLCC32 [CX2032]  
M29W004B@TSOP40 [CX1006]  
M29W004BT@TSOP40 [CX1006]  
M29W008AB@TSOP40 [CX1006]  
M29W008B@TSOP40 [CX1006]  
M29W010B@PLCC32 [CX2032]  
M29W017D@FBGA48 [CX5022]  
M29W022BB [CX0001]  
M29W022BB@TSOP32 [CX1002]  
M29W022BT@PLCC32 [CX2032]  
M29W040@PLCC32 [CX2032]  
M29W040B@PLCC32 [CX2032]  
M29W064FB@FBGA48 [CX5002]  
M29W064FT@FBGA48 [CX5002]  
M29W102BB@TSOP40 [CX1005]  
M29W116BB@TSOP40 [CX1006]  
M29W128GH@FBGA64 [CX5004]  
M29W128GL@FBGA64 [CX5004]  
M29W128GSH@FBGA64 [CX5004]  
M29W128GSH@TSOP56 [CX1055]  
M29W128GSL@FBGA64(ZS) [CX5074]  
M29W160BB@LBGA48 [CX5022]  
M29W160BB@TSOP48 [CX1004]  
M29W160BT@PSOP44 [CX1014]  
M29W160DB@LBGA48 [CX5022]  
M29W160DB@TSOP48 [CX1004]  
M29W160DT@PSOP44 [CX1014]  
M29W160EB@LBGA48 [CX5002]  
M29W160EB@PSOP44 [CX1014]  
M29W160ET@LBGA48 [CX5002]  
M29W160ET@PSOP44 [CX1014]  
M29W160FB@LBGA48 [CX5002]  
M29W160FT@LBGA48 [CX5002]  
M29W200BB@PSOP44 [CX1014]  
M29W200BT@PSOP44 [CX1014]  
M29W256AD@FBGA48 [CX0001]  
M29W256ADP@FBGA44 [CX5056]  
M29W256AP@FBGA88 [CX5005]  
M29W256GH@LFBGA64 [CX5074]  
M29W256GH@TSOP56 [CX1055]  
M29W256GL@TFBGA64 [CX5004]  
M29W256JD@FBGA64 [CX5004]

M29W256JD@TSOP56 [CX1011]  
M29W256JP@TSOP56 [CX1011]  
M29W256LP@FBGA56 [CX5056]  
M29W256PD@FBGA64 [CX5004]  
M29W256PP@FBGA64 [CX5004]  
M29W256TD@FBGA48 [CX5005]  
M29W256TD@TSOP48 [CX1004]  
M29W256TP@FBGA64 [CX5004]  
M29W256TP@TSOP56 [CX1011]  
M29W320DB@FBGA63 [CX5047]  
M29W320DT@FBGA48 [CX5002]  
M29W320DT@TSOP48 [CX1004]  
M29W320EB@FBGA64 [CX5074]  
M29W320ET@FBGA48 [CX5002]  
M29W320ET@TSOP48 [CX1004]  
M29W320FT@TSOP48 [CX1004]  
M29W400B@TSOP48 [CX1004]  
M29W400BB@PSOP44 [CX1014]  
M29W400BT@LBGA48 [CX5002]  
M29W400BT@TSOP48 [CX1004]  
M29W400DB(ZE)@LBGA48 [CX5002]  
M29W400DB@TSOP48 [CX1004]  
M29W400DT(ZE)@LBGA48 [CX5002]  
M29W400DT@TSOP48 [CX1004]  
M29W400T@TSOP48 [CX1004]  
M29W512B@TSOP32 [CX1003]  
M29W512TD@FBGA48 [CX5005]  
M29W512TD@TSOP48 [CX0001]  
M29W640DB@FBGA63 [CX5047]  
M29W640DT@FBGA63 [CX5047]  
M29W640FB(Q\_Word)@FBGA48 [CX5002]  
M29W640FB(Q\_Word)@TSOP48 [CX1004]  
M29W640FB@FBGA48 [CX5002]  
M29W640FT(Q\_Word)@FBGA48 [CX5002]  
M29W640FT(Q\_Word)@TSOP48 [CX1004]  
M29W640FT@FBGA48 [CX5002]  
M29W640GB(Mirror)@FBGA48 [CX5002]  
M29W640GB(Mirror)@FBGA64 [CX5004]  
M29W640GB(Mirror)@TSOP48 [CX1004]  
M29W640GB(Mirror)@TSOP56 [CX1011]  
M29W640GB(Q\_Word)@FBGA48 [CX5002]  
M29W640GB(Q\_Word)@FBGA64 [CX5004]  
M29W640GB(Q\_Word)@TSOP48 [CX1004]  
M29W640GB(Q\_Word)@TSOP56 [CX1011]  
M29W640GH(Mirror)@FBGA48 [CX5002]  
M29W640GH(Mirror)@FBGA64 [CX5004]  
M29W640GH(Mirror)@TSOP48 [CX1004]  
M29W640GH(Mirror)@TSOP56 [CX1011]  
M29W640GH(Q\_Word)@FBGA48 [CX5002]  
M29W640GH(Q\_Word)@FBGA64 [CX5004]  
M29W640GH(Q\_Word)@TSOP48 [CX1004]  
M29W640GH(Q\_Word)@TSOP56 [CX1011]  
M29W640GL(Mirror)@FBGA48 [CX5002]  
M29W640GL(Mirror)@FBGA64 [CX5004]  
M29W640GL(Mirror)@TSOP48 [CX1004]  
M29W640GL(Mirror)@TSOP56 [CX1011]  
M29W640GL(Q\_Word)@FBGA48 [CX5002]  
M29W640GL(Q\_Word)@FBGA64 [CX5004]  
M29W640GL(Q\_Word)@TSOP48 [CX1004]

M29W256JP@FBGA64 [CX5004]  
M29W256LP@FBGA48 [CX0001]  
M29W256LP@FBGA88 [CX5005]  
M29W256PD@TSOP56 [CX1011]  
M29W256PP@TSOP56 [CX1011]  
M29W256TD@FBGA64 [CX5004]  
M29W256TD@TSOP56 [CX1011]  
M29W256TP@TSOP48 [CX1004]  
M29W320DB@FBGA48 [CX5002]  
M29W320DB@TSOP48 [CX1004]  
M29W320DT@FBGA63 [CX5047]  
M29W320EB@FBGA48 [CX5002]  
M29W320EB@TSOP48 [CX1004]  
M29W320ET@FBGA64 [CX5074]  
M29W320FB@TSOP48 [CX1004]  
M29W400B@PSOP44 [CX1014]  
M29W400BB@LBGA48 [CX5002]  
M29W400BB@TSOP48 [CX1004]  
M29W400BT@PSOP44 [CX1014]  
M29W400DB(ZA)@LBGA48 [CX5039]  
M29W400DB@PSOP44 [CX1014]  
M29W400DT(ZA)@LBGA48 [CX5039]  
M29W400DT@PSOP44 [CX1014]  
M29W400T@PSOP44 [CX1014]  
M29W512B@PLCC32 [CX2032]  
M29W512G2G@TSOP56 [CX0051]  
M29W512TD@FBGA64 [CX5004]  
M29W512TD@TSOP56 [CX1011]  
M29W640DB@TSOP48 [CX1004]  
M29W640DT@TSOP48 [CX1004]  
  
M29W640FB@TSOP48 [CX1004]  
  
M29W640FT@TSOP48 [CX1004]

M29W640GL(Q\_Word)@TSOP56 [CX1011]  
M29W640GLH(Mirror)@FBGA48 [CX5002]  
M29W640GLT(Mirror)@FBGA48 [CX5002]  
M29W640GSB(Mirror)@FBGA48 [CX5002]  
M29W640GSB(Mirror)@FBGA64 [CX5004]  
M29W640GSB(Mirror)@TSOP48 [CX1004]  
M29W640GSB(Mirror)@TSOP56 [CX1011]  
M29W640GSB(Q\_Word)@FBGA48 [CX5002]  
M29W640GSB(Q\_Word)@FBGA64 [CX5004]  
M29W640GSB(Q\_Word)@TSOP48 [CX1004]  
M29W640GSB(Q\_Word)@TSOP56 [CX1011]  
M29W640GSH(Mirror)@FBGA48 [CX5002]  
M29W640GSH(Mirror)@FBGA64 [CX5004]  
M29W640GSH(Mirror)@TSOP48 [CX1004]  
M29W640GSH(Mirror)@TSOP56 [CX1011]  
M29W640GSH(Q\_Word)@FBGA48 [CX5002]  
M29W640GSH(Q\_Word)@FBGA64 [CX5004]  
M29W640GSH(Q\_Word)@TSOP48 [CX1004]  
M29W640GSH(Q\_Word)@TSOP56 [CX1011]  
M29W640GSL(Mirror)@FBGA64 [CX5004]  
M29W640GSL(Mirror)@TSOP48 [CX1004]  
M29W640GSL(Mirror)@TSOP56 [CX1011]  
M29W640GSL(Q\_Word)@FBGA48 [CX5002]  
M29W640GSL(Q\_Word)@FBGA64 [CX5004]  
M29W640GSL(Q\_Word)@TSOP48 [CX1004]  
M29W640GSL(Q\_Word)@TSOP56 [CX1011]  
M29W640GST(Mirror)@FBGA64 [CX5004]  
M29W640GST(Mirror)@TSOP48 [CX1004]  
M29W640GST(Mirror)@TSOP56 [CX1011]  
M29W640GST(Q\_Word)@FBGA48 [CX5002]  
M29W640GST(Q\_Word)@FBGA64 [CX5004]  
M29W640GST(Q\_Word)@TSOP48 [CX1004]  
M29W640GST(Q\_Word)@TSOP56 [CX1011]  
M29W640GT(Mirror)@FBGA48 [CX5002]  
M29W640GT(Mirror)@FBGA64 [CX5004]  
M29W640GT(Mirror)@TSOP48 [CX1004]  
M29W640GT(Mirror)@TSOP56 [CX1011]  
M29W640GT(Q\_Word)@FBGA48 [CX5002]  
M29W640GT(Q\_Word)@FBGA64 [CX5004]  
M29W640GT(Q\_Word)@TSOP48 [CX1004]  
M29W640GT(Q\_Word)@TSOP56 [CX1011]  
M29W641DH@TSOP48 [CX1004]  
M29W641DU@FBGA63 [CX5047]  
M29W800AB@PSOP44 [CX1014]  
M29W800AT@LBGA48 [CX5039]  
M29W800AT@TSOP48 [CX1004]  
M29W800B@TSOP48 [CX1004]  
M29W800DB@PSOP44 [CX1014]  
M29W800DT@FBGA48 [CX5002]  
M29W800DT@TSOP48 [CX1004]  
M29W800T@TSOP48 [CX1004]  
M30L0R7000T0@FBGA88 [CX5005]  
M30L0R8000B2@FBGA88 [CX5005]  
M30L0R8000T2@FBGA88 [CX5005]  
M30L0T8800T0@FBGA88 [CX5005]  
M30W0R6600D0@LFBGA88 [CX5005]  
M30WR128B@LFBGA88 [CX5005]  
M34C02@MSOP8 [CX4002]  
M34C02@TSOP8 [CX1059]  
M29W641DL@TSOP48 [CX1004]  
M29W800AB@LBGA48 [CX5039]  
M29W800AB@TSOP48 [CX1004]  
M29W800AT@PSOP44 [CX1014]  
M29W800B@PSOP44 [CX1014]  
M29W800DB@FBGA48 [CX5002]  
M29W800DB@TSOP48 [CX1004]  
M29W800DT@PSOP44 [CX1014]  
M29W800T@PSOP44 [CX1014]  
M30L0R7000B0@FBGA88 [CX5005]  
M30L0R8000B0@FBGA88 [CX5005]  
M30L0R8000T0@FBGA88 [CX5005]  
M30L0T8800B0@FBGA88 [CX5005]  
M30W0R6600B0@LFBGA88 [CX5005]  
M30W0R6600T0@LFBGA88 [CX5005]  
M34C02 [CX0001]  
M34C02@SOIC8 [CX1045]  
M34D32 [CX0001]

M34D32@SOIC8 [CX1045]  
M34D64 [CX0001]  
M34D64@TSSOP8 [CX1059]  
M34E02@MSOP8 [CX1015]  
M34E02@TSOP8 [CX1059]  
M35080@SOIC8 [CX1045]  
M36A0W5020T0@FBGA66 [CX5026]  
M36A0W5030T0@FBGA66 [CX5026]  
M36A0W5040B1@FBGA66 [CX5026]  
M36A0W5040T1@FBGA66 [CX5026]  
M36C0W5030T0@FBGA56 [CX5045]  
M36C0W5040T0@FBGA56 [CX5045]  
M36C0W6040T0@FBGA56 [CX5045]  
M36C0W6050T0@FBGA56 [CX5045]  
M36D0R5030B0(EFP)@FBGA67 [CX5026]  
M36D0R5030B0(Q\_Word)@FBGA67 [CX5026]  
M36D0R5030T0(EFP)@FBGA67 [CX5026]  
M36D0R5030T0(Q\_Word)@FBGA67 [CX5026]  
M36D0R5040B0(EFP)@FBGA67 [CX5026]  
M36D0R5040B0(Q\_Word)@FBGA67 [CX5026]  
M36D0R5040T0(EFP)@FBGA67 [CX5026]  
M36D0R5040T0(Q\_Word)@FBGA67 [CX5026]  
M36D0R6040B0(EFP)@FBGA67 [CX5026]  
M36D0R6040B0(Q\_Word)@FBGA67 [CX5026]  
M36D0R6040T0(EFP)@FBGA67 [CX5026]  
M36D0R6040T0(Q\_Word)@FBGA67 [CX5026]  
M36DR232A@FBGA66 [CX5026]  
M36DR432AD@FBGA66 [CX5026]  
M36L0R7040B0@FBGA88 [CX5005]  
M36L0R7050B0@FBGA88 [CX5005]  
M36L0R7050B2@FBGA88 [CX5005]  
M36L0R7050L1@FBGA88 [CX5005]  
M36L0R7050L3@FBGA56 [CX5099]  
M36L0R7050T0@FBGA88 [CX5005]  
M36L0R7050T2@FBGA88 [CX5005]  
M36L0R7050U1@FBGA88 [CX5005]  
M36L0R7050U3@FBGA56 [CX5099]  
M36L0R7060B1@FBGA88 [CX5005]  
M36L0R7060L1@FBGA88 [CX5005]  
M36L0R7060L3@FBGA88 [CX5005]  
M36L0R7060T2@FBGA88 [CX5005]  
M36L0R7060U3@FBGA56 [CX5099]  
M36L0R8050L3@FBGA56 [CX5099]  
M36L0R8050U3@FBGA56 [CX5099]  
M36L0R8060B0@FBGA88 [CX5005]  
M36L0R8060B3@FBGA88 [CX5005]  
M36L0R8060B8@FBGA88 [CX5005]  
M36L0R8060L0@FBGA88 [CX5005]  
M36L0R8060L3@FBGA80 [CX5052]  
M36L0R8060T0@FBGA88 [CX5005]  
M36L0R8060T3@FBGA88 [CX5005]  
M36L0R8060T8@FBGA88 [CX5005]  
M36L0R8060U0@FBGA88 [CX5005]  
M36L0R8060U3@FBGA80 [CX5052]  
M36L0T7040B0@FBGA88 [CX5005]  
M36L0T7050B0@FBGA88 [CX5005]  
M36L0T7050B2@FBGA88 [CX5005]  
M36L0T7050T0@FBGA88 [CX5005]  
M36L0T7050T2@FBGA88 [CX5005]  
M34D32@TSSOP8 [CX1059]  
M34D64@SOIC8 [CX1045]  
M34E02 [CX0001]  
M34E02@SOIC8 [CX1045]  
M35080 [CX0001]  
M36A0W5020B0@FBGA66 [CX5026]  
M36A0W5030B0@FBGA66 [CX5026]  
M36A0W5040B0@FBGA66 [CX5026]  
M36A0W5040T0@FBGA66 [CX5026]  
M36C0W5030B0@FBGA56 [CX5045]  
M36C0W5040B0@FBGA56 [CX5045]  
M36C0W6040B0@FBGA56 [CX5045]  
M36C0W6050B0@FBGA56 [CX5045]  
M36C0W6050T0@FBGA56(XW) [CX5005]  
M36DR232B@FBGA66 [CX5026]  
M36DR432BD@FBGA66 [CX5026]  
M36L0R7040T0@FBGA88 [CX5005]  
M36L0R7050B1@FBGA88 [CX5005]  
M36L0R7050B4@FBGA88 [CX5005]  
M36L0R7050L2@FBGA88 [CX5005]  
M36L0R7050L3@FBGA88 [CX5005]  
M36L0R7050T1@FBGA88 [CX5005]  
M36L0R7050T4@FBGA88 [CX5005]  
M36L0R7050U2@FBGA88 [CX5005]  
M36L0R7050U3@FBGA88 [CX5005]  
M36L0R7060B2@FBGA88 [CX5005]  
M36L0R7060L3@FBGA56 [CX5099]  
M36L0R7060T1@FBGA88 [CX5005]  
M36L0R7060U1@FBGA88 [CX5005]  
M36L0R7060U3@FBGA88 [CX5005]  
M36L0R8050L3@FBGA88 [CX5005]  
M36L0R8050U3@FBGA88 [CX5005]  
M36L0R8060B1@FBGA88 [CX5005]  
M36L0R8060B5@FBGA88 [CX5005]  
M36L0R8060B9@FBGA88 [CX5005]  
M36L0R8060L3@FBGA56 [CX5099]  
M36L0R8060L3@FBGA88 [CX5005]  
M36L0R8060T1@FBGA88 [CX5005]  
M36L0R8060T5@FBGA88 [CX5005]  
M36L0R8060T9@FBGA88 [CX5005]  
M36L0R8060U3@FBGA56 [CX5099]  
M36L0R8060U3@FBGA88 [CX5005]  
M36L0T7040T0@FBGA88 [CX5005]  
M36L0T7050B1@FBGA88 [CX5005]  
M36L0T7050B3@FBGA88 [CX5005]  
M36L0T7050T1@FBGA88 [CX5005]  
M36L0T7050T3@FBGA88 [CX5005]

M36L0T7060B0@FBGA88 [CX5005] M36L0T7060B1@FBGA88 [CX5005]  
M36L0T7060B2@FBGA88 [CX5005] M36L0T7060B3@FBGA88 [CX5005]  
M36L0T7060T0@FBGA88 [CX5005] M36L0T7060T1@FBGA88 [CX5005]  
M36L0T7060T2@FBGA88 [CX5005] M36L0T7060T3@FBGA88 [CX5005]  
M36L0T8050B0@FBGA88 [CX5005] M36L0T8050B1@FBGA88 [CX5005]  
M36L0T8050B3@FBGA88 [CX5005] M36L0T8050T0@FBGA88 [CX5005]  
M36L0T8050T1@FBGA88 [CX5005] M36L0T8050T3@FBGA88 [CX5005]  
M36L0T8060B0@FBGA88 [CX5005] M36L0T8060B1@FBGA88 [CX5005]  
M36L0T8060B3@FBGA88 [CX5005] M36L0T8060T0@FBGA88 [CX5005]  
M36L0T8060T1@FBGA88 [CX5005] M36L0T8060T3@FBGA88 [CX5005]  
M36LLR7750B0@FBGA88 [CX5005] M36LLR7750D0@FBGA88 [CX5005]  
M36LLR7750T0@FBGA88 [CX5005] M36LLR7760B0@FBGA88 [CX5005]  
M36LLR7760D0@FBGA88 [CX5005] M36LLR7760T0@FBGA88 [CX5005]  
M36LLR8760B1@FBGA88 [CX5005] M36LLR8760D1@FBGA88 [CX5005]  
M36LLR8760M1@FBGA88 [CX5005] M36LLR8760T1@FBGA88 [CX5005]  
M36LLR8860B1@FBGA88 [CX5001] M36LLR8860D1@FBGA88 [CX5001]  
M36LLR8860M1@FBGA88 [CX5001] M36LLR8860T1@FBGA88 [CX5001]  
M36LLR8870B0@FBGA88 [CX5001] M36LLR8870B1@FBGA88 [CX5001]  
M36LLR8870D0@FBGA88 [CX5001] M36LLR8870D1@FBGA88 [CX5001]  
M36LLR8870M0@FBGA88 [CX5001] M36LLR8870M1@FBGA88 [CX5001]  
M36LLR8870T0@FBGA88 [CX5001] M36LLR8870T1@FBGA88 [CX5001]  
M36W0R5020B0(EFP)@FBGA88 [CX5005]  
M36W0R5020B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5020T0(EFP)@FBGA88 [CX5005]  
M36W0R5020T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5030B0(EFP)@FBGA88 [CX5005]  
M36W0R5030B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5030T0(EFP)@FBGA88 [CX5005]  
M36W0R5030T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5030U5@TFBGA52 [CX5127] M36W0R5030U5@TFBGA88 [CX5005]  
M36W0R5040B0(EFP)@FBGA88 [CX5005]  
M36W0R5040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B1(EFP)@FBGA88 [CX5005]  
M36W0R5040B1(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B2(EFP)@FBGA88 [CX5005]  
M36W0R5040B2(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B4(EFP)@FBGA88 [CX5005]  
M36W0R5040B4(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B5(EFP)@FBGA88 [CX5005]  
M36W0R5040B5(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040B7(EFP)@FBGA88 [CX5005]  
M36W0R5040B7(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040L3@FBGA88 [CX5005] M36W0R5040L4@TFBGA56 [CX5099]  
M36W0R5040L4@TFBGA88 [CX5005] M36W0R5040L6@TFBGA52 [CX5127]  
M36W0R5040L6@TFBGA88 [CX5005]  
M36W0R5040T0(EFP)@FBGA88 [CX5005]  
M36W0R5040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T1(EFP)@FBGA88 [CX5005]  
M36W0R5040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T2(EFP)@FBGA88 [CX5005]  
M36W0R5040T2(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T4(EFP)@FBGA88 [CX5005]  
M36W0R5040T4(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T5(EFP)@FBGA88 [CX5005]  
M36W0R5040T5(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040T7(EFP)@FBGA88 [CX5005]  
M36W0R5040T7(Q\_Word)@FBGA88 [CX5005]  
M36W0R5040U3@FBGA88 [CX5005] M36W0R5040U4@TFBGA56 [CX5099]  
M36W0R5040U4@TFBGA88 [CX5005] M36W0R5040U5@TFBGA52 [CX5127]



M36W0R5040U5@TFBGA88 [CX5005] M36W0R5040U6@TFBGA52 [CX5127]  
M36W0R5040U6@TFBGA88 [CX5005] M36W0R5050L6@TFBGA52 [CX5127]  
M36W0R5050L6@TFBGA88 [CX5005] M36W0R5050U6@TFBGA52 [CX5127]  
M36W0R5050U6@TFBGA88 [CX5005]  
M36W0R6030B0(EFP)@FBGA88 [CX5005]  
M36W0R6030B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6030T0(EFP)@FBGA88 [CX5005]  
M36W0R6030T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B0(EFP)@FBGA88 [CX5005]  
M36W0R6040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B1(EFP)@FBGA88 [CX5005]  
M36W0R6040B1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B3(EFP)@FBGA88 [CX5005]  
M36W0R6040B3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B4(EFP)@FBGA88 [CX5005]  
M36W0R6040B4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040B7(EFP)@FBGA88 [CX5005]  
M36W0R6040B7(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040L3@FBGA88 [CX5005] M36W0R6040L4@TFBGA56 [CX5099]  
M36W0R6040L4@TFBGA88 [CX5005] M36W0R6040L6@TFBGA52 [CX5127]  
M36W0R6040L6@TFBGA88 [CX5005]  
M36W0R6040T0(EFP)@FBGA88 [CX5005]  
M36W0R6040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T1(EFP)@FBGA88 [CX5005]  
M36W0R6040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T3(EFP)@FBGA88 [CX5005]  
M36W0R6040T3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T4(EFP)@FBGA88 [CX5005]  
M36W0R6040T4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040T7(EFP)@FBGA88 [CX5005]  
M36W0R6040T7(Q\_Word)@FBGA88 [CX5005]  
M36W0R6040U3@FBGA88 [CX5005] M36W0R6040U4@TFBGA56 [CX5099]  
M36W0R6040U4@TFBGA88 [CX5005] M36W0R6040U5@TFBGA52 [CX5127]  
M36W0R6040U5@TFBGA88 [CX5005] M36W0R6040U6@TFBGA52 [CX5127]  
M36W0R6040U6@TFBGA88 [CX5005]  
M36W0R6050B0(EFP)@FBGA88 [CX5005]  
M36W0R6050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050B1(EFP)@FBGA88 [CX5005]  
M36W0R6050B1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050B3(EFP)@FBGA88 [CX5005]  
M36W0R6050B3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050B4(EFP)@FBGA88 [CX5005]  
M36W0R6050B4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050L0@FBGA88 [CX5005] M36W0R6050L4@TFBGA56 [CX5099]  
M36W0R6050L4@TFBGA88 [CX5005] M36W0R6050L6@TFBGA52 [CX5127]  
M36W0R6050L6@TFBGA88 [CX5005]  
M36W0R6050T0(EFP)@FBGA88 [CX5005]  
M36W0R6050T0(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050T1(EFP)@FBGA88 [CX5005]  
M36W0R6050T1(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050T3(EFP)@FBGA88 [CX5005]  
M36W0R6050T3(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050T4(EFP)@FBGA88 [CX5005]  
M36W0R6050T4(Q\_Word)@FBGA88 [CX5005]  
M36W0R6050U0@FBGA88 [CX5005] M36W0R6050U4@TFBGA56 [CX5099]  
M36W0R6050U4@TFBGA88 [CX5005] M36W0R6050U5@TFBGA56 [CX5099]  
M36W0R6050U5@TFBGA88 [CX5005] M36W0R6050U6@TFBGA52 [CX5127]  
M36W0R6050U6@TFBGA88 [CX5005]  
M36W0R7050B0(EFP)@FBGA88 [CX5005]

M36W0R7050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0R7050T0(EFP)@FBGA88 [CX5005]  
M36W0R7050T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T5040B1(EFP)@FBGA88 [CX5005]  
M36W0T5040B1(Q\_Word)@FBGA88 [CX5005]  
M36W0T5040T1(EFP)@FBGA88 [CX5005]  
M36W0T5040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0T6030B0(EFP)@FBGA88 [CX5005]  
M36W0T6030B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6030T0(EFP)@FBGA88 [CX5005]  
M36W0T6030T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040B0(EFP)@FBGA88 [CX5005]  
M36W0T6040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040B1(EFP)@FBGA88 [CX5005]  
M36W0T6040B1(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040B3(EFP)@FBGA88 [CX5005]  
M36W0T6040B3(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040T0(EFP)@FBGA88 [CX5005]  
M36W0T6040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040T1(EFP)@FBGA88 [CX5005]  
M36W0T6040T1(Q\_Word)@FBGA88 [CX5005]  
M36W0T6040T3(EFP)@FBGA88 [CX5005]  
M36W0T6040T3(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050B0(EFP)@FBGA88 [CX5005]  
M36W0T6050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050B3(EFP)@FBGA88 [CX5005]  
M36W0T6050B3(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050T0(EFP)@FBGA88 [CX5005]  
M36W0T6050T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T6050T3(EFP)@FBGA88 [CX5005]  
M36W0T6050T3(Q\_Word)@FBGA88 [CX5005]  
M36W0T7040B0(EFP)@FBGA88 [CX5005]  
M36W0T7040B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T7040T0(EFP)@FBGA88 [CX5005]  
M36W0T7040T0(Q\_Word)@FBGA88 [CX5005]  
M36W0T7050B0(EFP)@FBGA88 [CX5005]  
M36W0T7050B0(Q\_Word)@FBGA88 [CX5005]  
M36W0T7050T0(EFP)@FBGA88 [CX5005]  
M36W0T7050T0(Q\_Word)@FBGA88 [CX5005]  
M36W216BI@LFBGA66 [CX5026] M36W216TI@LFBGA66 [CX5026]  
M36W416BG@LFBGA66 [CX5026] M36W416TG@LFBGA66 [CX5026]  
M36W432B@LFBGA66 [CX5026] M36W432BG@LFBGA66 [CX5026]  
M36W432T@FBGA66 [CX5026] M36W432TG@LFBGA66 [CX5026]  
M36W832BE@FBGA67 [CX5026] M36W832TE@FBGA67 [CX5026]  
M36W864BE@FBGA67 [CX5026] M36W864TE@FBGA67 [CX5026]  
M36WWR6650B0@LFBGA88 [CX5005] M36WWR6650D0@LFBGA88 [CX5005]  
M36WWR6650T0@LFBGA88 [CX5005] M45PE10@SOIC8 [CX1045#4]  
M45PE10@VQFPN8 [CX4005#4] M45PE16@SOIC8 [CX1044#4]  
M45PE16@VQFPN8 [CX4005#4] M45PE20@SOIC8 [CX1045#4]  
M45PE20@SOIC8(ISP) [CX0001] M45PE20@VQFPN8 [CX4005#4]  
M45PE20@VQFPN8(ISP) [CX0001] M45PE40@SOIC8 [CX1044#4]  
M45PE40@SOIC8(ISP) [CX0001] M45PE40@VQFPN8 [CX4005#4]  
M45PE40@VQFPN8(ISP) [CX0001] M45PE80@SOIC16 [CX1033#4]  
M45PE80@SOIC16(ISP) [CX0001] M45PE80@SOIC8 [CX1044#4]  
M45PE80@SOIC8(ISP) [CX0001] M45PE80@VQFPN8 [CX4005#4]  
M45PE80@VQFPN8(ISP) [CX0001] M48C02 [CX0001]  
M48C02B [CX0001] M48C12 [CX0001]  
M48C12B [CX0001] M48T02 [CX0001]  
M48T02B [CX0001] M48T08 [CX0001]

M48T12 [CX0001] M48T128V [CX0001]  
M48T128Y [CX0001] M48T129V [CX0001]  
M48T129Y [CX0001] M48T12B [CX0001]  
M48T18 [CX0001] M48T30 [CX0001]  
M48T30Y [CX0001] M48T32 [CX0001]  
M48T32Y [CX0001] M48T35 [CX0001]  
M48T35@SOIC28 [CX1033] M48T35AV [CX0001]  
M48T35AV@SOIC28 [CX1033] M48T35AY [CX0001]  
M48T35AY@SOIC28 [CX1033] M48T35Y [CX0001]  
M48T35Y@SOIC28 [CX1033] M48T512AV [CX0001]  
M48T512AY [CX0001] M48T512V [CX0001]  
M48T512Y [CX0001] M48T513V [CX0001]  
M48T513Y [CX0001] M48T559 [CX0001]  
M48T559@SOIC28 [CX1035] M48T559Y [CX0001]  
M48T559Y@SOIC28 [CX1035] M48T58 [CX0001]  
M48T58@SOIC28 [CX1033] M48T58Y [CX0001]  
M48T58Y@SOIC28 [CX1033] M48T59 [CX0001]  
M48T59@SOIC28 [CX1033] M48T59V [CX0001]  
M48T59V@SOIC28 [CX1033] M48T59Y [CX0001]  
M48T59Y@SOIC28 [CX1033] M48Z02 [CX0001]  
M48Z02B [CX0001] M48Z08 [CX0001]  
M48Z12 [CX0001] M48Z128 [CX0001]  
M48Z128V [CX0001] M48Z128Y [CX0001]  
M48Z129V [CX0001] M48Z129Y [CX0001]  
M48Z12B [CX0001] M48Z18 [CX0001]  
M48Z30 [CX0001] M48Z30Y [CX0001]  
M48Z32 [CX0001] M48Z32Y [CX0001]  
M48Z35 [CX0001] M48Z35@SOIC28 [CX1033]  
M48Z35Y [CX0001] M48Z35Y@SOIC28 [CX1033]  
M48Z512AV [CX0001] M48Z512AY [CX0001]  
M48Z512V [CX0001] M48Z512Y [CX0001]  
M48Z513V [CX0001] M48Z513Y [CX0001]  
M48Z58 [CX0001] M48Z58@SOIC28 [CX1033]  
M48Z58Y [CX0001] M48Z58Y@SOIC28 [CX1033]  
M48Z59 [CX0001] M48Z59@SOIC28 [CX1033]  
M48Z59W [CX0001] M48Z59W@SOIC28 [CX1033]  
M48Z59Y [CX0001] M48Z59Y@SOIC28 [CX1033]  
M50FLW040A@PLCC32 [CX2032] M50FLW040A@TSOP40 [CX1006]  
M50FLW040A@VSOP32 [CX1003] M50FLW040B@PLCC32 [CX2032]  
M50FLW040B@TSOP40 [CX1006] M50FLW040B@VSOP32 [CX1003]  
M50FLW080A@PLCC32 [CX2032] M50FLW080A@TSOP40 [CX1006]  
M50FLW080A@VSOP32 [CX1003] M50FLW080B@PLCC32 [CX2032]  
M50FLW080B@TSOP40 [CX1006] M50FLW080B@VSOP32 [CX1003]  
M50FW002@PLCC32 [CX2032] M50FW016@TSOP40 [CX1006]  
M50FW020@PLCC32 [CX2032] M50FW040@PLCC32 [CX2032]  
M50FW040@TSOP40 [CX1006] M50FW080@PLCC32 [CX2032]  
M50FW080@TSOP40 [CX1006] M50FW080@VSOP32 [CX1003]  
M50LPW002@PLCC32 [CX2032] M50LPW012@PLCC32 [CX2032]  
M50LPW020@PLCC32 [CX2032] M50LPW040@PLCC32 [CX2032]  
M50LPW040@TSOP40 [CX1006] M50LPW041@PLCC32 [CX2032]  
M50LPW041@TSOP40 [CX1006] M50LPW080@PLCC32 [CX2032]  
M50LPW080@TSOP40 [CX1006] M50LPW116@TSOP40 [CX1006]  
M58BW016DB@PQFP80(Big endian) [CX3020]  
M58BW016DB@PQFP80(Little endian) [CX3020]  
M58BW016DT@PQFP80(Big endian) [CX3020]  
M58BW016DT@PQFP80(Little endian) [CX3020]  
M58LR128FB@VFPGA56 [CX5032] M58LR128FT@VFPGA56 [CX5032]  
M58LR128GB@VFPGA56 [CX5032] M58LR128GL@FBGA44 [CX5068]  
M58LR128GT@VFPGA56 [CX5032] M58LR128GU@FBGA44 [CX5068]

M58LR128HB@VFBGA56 [CX5032]  
M58LR128KB@FBGA56 [CX5032]  
M58LR128KT@FBGA56 [CX5032]  
M58LR256GL@FBGA44 [CX5068]  
M58LR256KB@FBGA79 [CX5164]  
M58LR256KT@FBGA79 [CX5164]  
M58LT128GB@FBGA56 [CX5032]  
M58LT128GST@FBGA64 [CX5004]  
M58LT128HSB@FBGA64 [CX5004]  
M58LT128KSB@FBGA64 [CX5004]  
M58LT256GB@FBGA64 [CX5004]  
M58LT256JSB@FBGA64 [CX5004]  
M58LT256KSB@FBGA64 [CX5004]  
M58LW032A@FBGA64 [CX5004]  
M58LW032C@FBGA64 [CX5004]  
M58LW032D@FBGA64 [CX5004]  
M58LW064C@FBGA64 [CX5004]  
M58LW064D@FBGA64 [CX5004]  
M58LW128A@FBGA64 [CX5004]  
M58WR016KB(EFP)@FBGA56 [CX5032]  
M58WR016KB(Q\_Word)@FBGA56 [CX5032]  
M58WR016KB(Q\_Word)@FBGA88 [CX5005]  
M58WR016KL@FBGA44 [CX5176]  
M58WR016KT(EFP)@FBGA88 [CX5005]  
M58WR016KT(Q\_Word)@FBGA56 [CX5032]  
M58WR016KT(Q\_Word)@FBGA88 [CX5005]  
M58WR016KU@FBGA44 [CX5176]  
M58WR016QB(Q\_Word)@FBGA56 [CX5032]  
M58WR016QL@FBGA44 [CX5176]  
M58WR016QT(Q\_Word)@FBGA56 [CX5032]  
M58WR016QU@FBGA44 [CX5176]  
M58WR032EB(Q\_Word)@FBGA56 [CX5032]  
M58WR032ET(EFP)@FBGA56 [CX5032]  
M58WR032ET(Q\_Word)@FBGA56 [CX5032]  
M58WR032FB(EFP)@FBGA56 [CX5032]  
M58WR032FB(Q\_Word)@FBGA56 [CX5032]  
M58WR032FT(EFP)@FBGA56 [CX5032]  
M58WR032FT(Q\_Word)@FBGA56 [CX5032]  
M58WR032HB(EFP)@FBGA56 [CX5032]  
M58WR032HB(Q\_Word)@FBGA56 [CX5032]  
M58WR032HT(EFP)@FBGA56 [CX5032]  
M58WR032HT(Q\_Word)@FBGA56 [CX5032]  
M58WR032KB(EFP)@FBGA56 [CX5032]  
M58WR032KB(Q\_Word)@FBGA56 [CX5032]  
M58WR032KB(Q\_Word)@FBGA88 [CX5005]  
M58WR032KL@FBGA44 [CX5176]  
M58WR032KT(EFP)@FBGA88 [CX5005]  
M58WR032KT(Q\_Word)@FBGA56 [CX5032]  
M58WR032KT(Q\_Word)@FBGA88 [CX5005]  
M58WR032KU@FBGA44 [CX5176]  
M58WR032QB(Q\_Word)@FBGA56 [CX5032]  
M58WR032QL@FBGA44 [CX5176]  
M58WR032QT(Q\_Word)@FBGA56 [CX5032]  
M58WR032QU@FBGA44 [CX5176]  
M58WR064EB(Q\_Word)@FBGA56 [CX5032]  
M58WR064ET(EFP)@FBGA56 [CX5032]  
M58WR064ET(Q\_Word)@FBGA56 [CX5032]  
M58WR064FB(EFP)@FBGA56 [CX5032]  
M58WR064FB(Q\_Word)@FBGA56 [CX5032]

M58LR128HT@VFBGA56 [CX5032]  
M58LR128KB@FBGA88 [CX5005]  
M58LR128KT@FBGA88 [CX5005]  
M58LR256GU@FBGA44 [CX5068]  
M58LR256KB@FBGA88 [CX5005]  
M58LR256KT@FBGA88 [CX5005]  
M58LT128GSB@FBGA64 [CX5004]  
M58LT128GT@FBGA56 [CX5032]  
M58LT128HST@FBGA64 [CX5004]  
M58LT128KST@FBGA64 [CX5004]  
M58LT256GT@FBGA64 [CX5004]  
M58LT256JST@FBGA64 [CX5004]  
M58LT256KST@FBGA64 [CX5004]  
M58LW032A@TSOP56 [CX1011]  
M58LW032C@TSOP56 [CX1011]  
M58LW032D@TSOP56 [CX1011]  
M58LW064C@TSOP56 [CX1011]  
M58LW064D@TSOP56 [CX1011]  
M58LW128A@TSOP56 [CX1011]  
M58WR016KB(EFP)@FBGA88 [CX5005]  
M58WR016KT(EFP)@FBGA56 [CX5032]  
M58WR016QB(EFP)@FBGA56 [CX5032]  
M58WR016QT(EFP)@FBGA56 [CX5032]  
M58WR032EB(EFP)@FBGA56 [CX5032]  
M58WR032KB(EFP)@FBGA88 [CX5005]  
M58WR032KT(EFP)@FBGA56 [CX5032]  
M58WR032QB(EFP)@FBGA56 [CX5032]  
M58WR032QT(EFP)@FBGA56 [CX5032]  
M58WR064EB(EFP)@FBGA56 [CX5032]

M58WR064FT(EFP)@FBGA56 [CX5032]  
M58WR064FT(Q\_Word)@FBGA56 [CX5032]  
M58WR064HB(EFP)@FBGA56 [CX5032]  
M58WR064HB(Q\_Word)@FBGA56 [CX5032]  
M58WR064HL@FBGA44 [CX5066] M58WR064HT(EFP)@FBGA56 [CX5032]  
M58WR064HT(Q\_Word)@FBGA56 [CX5032]  
M58WR064HU@FBGA44 [CX5066] M58WR064KB(EFP)@FBGA56 [CX5032]  
M58WR064KB(EFP)@FBGA88 [CX5005]  
M58WR064KB(Q\_Word)@FBGA56 [CX5032]  
M58WR064KB(Q\_Word)@FBGA88 [CX5005]  
M58WR064KL@FBGA44 [CX5176] M58WR064KT(EFP)@FBGA56 [CX5032]  
M58WR064KT(EFP)@FBGA88 [CX5005]  
M58WR064KT(Q\_Word)@FBGA56 [CX5032]  
M58WR064KT(Q\_Word)@FBGA88 [CX5005]  
M58WR064KU@FBGA44 [CX5176] M58WR128FB(EFP)@FBGA56 [CX5032]  
M58WR128FB(Q\_Word)@FBGA56 [CX5032]  
M58WR128FT(EFP)@FBGA56 [CX5032]  
M58WR128FT(Q\_Word)@FBGA56 [CX5032]  
M58WT032KB(EFP)@FBGA88 [CX5005]  
M58WT032KB(Q\_Word)@FBGA88 [CX5005]  
M58WT032KT(EFP)@FBGA88 [CX5005]  
M58WT032KT(Q\_Word)@FBGA88 [CX5005]  
M58WT064KB(EFP)@FBGA88 [CX5005]  
M58WT064KB(Q\_Word)@FBGA88 [CX5005]  
M58WT064KT(EFP)@FBGA88 [CX5005]  
M58WT064KT(Q\_Word)@FBGA88 [CX5005]  
M59DR008E@FBGA48 [CX5060] M59DR008E@TSOP48 [CX1004]  
M59DR008F@FBGA48 [CX5060] M59DR008F@TSOP48 [CX1004]  
M59DR016C@FBGA48 [CX5060] M59DR016D@FBGA48 [CX5060]  
M59DR032A@FBGA48 [CX5060] M59DR032A@TSOP48 [CX1004]  
M59DR032B@FBGA48 [CX5060] M59DR032B@TSOP48 [CX1004]  
M59DR032EA@FBGA48 [CX5060] M59DR032EB@FBGA48 [CX5060]  
M59PW016 [CX0001] M59PW016@PSOP44 [CX1014]  
M59PW016@SDIP42 [CX0042] M59PW016@TSOP48 [CX1004]  
M59PW032@PSOP44 [CX1014] M59PW032@TSOP48 [CX1004]  
M59PW064@PSOP44 [CX1014] M59PW1282@PSOP44 [CX1014]  
M72DW64000B@FBGA73 [CX5001] M72DW75000C@FBGA73 [CX5001]  
M72DW75001C@FBGA73 [CX5001] M72DW76001D@FBGA73 [CX5001]  
M76DW52003BA@FBGA73 [CX5001] M76DW52003TA@FBGA73 [CX5001]  
M76DW52004BA@FBGA73 [CX5001] M76DW52004TA@FBGA73 [CX5001]  
M76DW62000A@FBGA73 [CX5001] M76DW63000A@FBGA73 [CX5001]  
M87C257 [CX0001] M87C257@PLCC32 [CX2032]  
M93C06(08bit) [CX0001] M93C06(08bit)@SOIC8 [CX1045]  
M93C06(16bit) [CX0001] M93C06(16bit)@SOIC8 [CX1045]  
M93C46(08bit) [CX0001] M93C46(08bit)@MLP8 [CX4001]  
M93C46(08bit)@MSOP8 [CX1015] M93C46(08bit)@SOIC8 [CX1045]  
M93C46(08bit)@TSSOP8 [CX1059] M93C46(16bit) [CX0001]  
M93C46(16bit)@MLP8 [CX4001] M93C46(16bit)@MSOP8 [CX1015]  
M93C46(16bit)@SOIC8 [CX1045] M93C46(16bit)@TSSOP8 [CX1059]  
M93C46R(08bit) [CX0001] M93C46R(08bit)@MLP8 [CX4001]  
M93C46R(08bit)@MSOP8 [CX1015] M93C46R(08bit)@SOIC8 [CX1045]  
M93C46R(08bit)@TSSOP8 [CX1059] M93C46R(16bit) [CX0001]  
M93C46R(16bit)@MLP8 [CX4001] M93C46R(16bit)@MSOP8 [CX1015]  
M93C46R(16bit)@SOIC8 [CX1045] M93C46R(16bit)@TSSOP8 [CX1059]  
M93C46W(08bit) [CX0001] M93C46W(08bit)@MLP8 [CX4001]  
M93C46W(08bit)@MSOP8 [CX1015] M93C46W(08bit)@SOIC8 [CX1045]  
M93C46W(08bit)@TSSOP8 [CX1059] M93C46W(16bit) [CX0001]  
M93C46W(16bit)@MLP8 [CX4001] M93C46W(16bit)@MSOP8 [CX1015]  
M93C46W(16bit)@SOIC8 [CX1045] M93C46W(16bit)@TSSOP8 [CX1059]

M93C56(08bit) [CX0001]  
M93C56(08bit)@MSOP8 [CX1015]  
M93C56(08bit)@TSSOP8 [CX1059]  
M93C56(16bit)@MLP8 [CX4001]  
M93C56(16bit)@SOIC8 [CX1045]  
M93C56R(08bit) [CX0001]  
M93C56R(08bit)@MSOP8 [CX1015]  
M93C56R(08bit)@TSSOP8 [CX1059]  
M93C56R(16bit)@MLP8 [CX4001]  
M93C56R(16bit)@SOIC8 [CX1045]  
M93C56W(08bit) [CX0001]  
M93C56W(08bit)@MSOP8 [CX1015]  
M93C56W(08bit)@TSSOP8 [CX1059]  
M93C56W(16bit)@MLP8 [CX4001]  
M93C56W(16bit)@SOIC8 [CX1045]  
M93C66(08bit) [CX0001]  
M93C66(08bit)@MSOP8 [CX1015]  
M93C66(08bit)@TSSOP8 [CX1059]  
M93C66(16bit)@MLP8 [CX4001]  
M93C66(16bit)@SOIC8 [CX1045]  
M93C66R(08bit) [CX0001]  
M93C66R(08bit)@MSOP8 [CX1015]  
M93C66R(08bit)@TSSOP8 [CX1059]  
M93C66R(16bit)@MLP8 [CX4001]  
M93C66R(16bit)@SOIC8 [CX1045]  
M93C66W(08bit) [CX0001]  
M93C66W(08bit)@MSOP8 [CX1015]  
M93C66W(08bit)@TSSOP8 [CX1059]  
M93C66W(16bit)@MLP8 [CX4001]  
M93C66W(16bit)@SOIC8 [CX1045]  
M93C76(08bit) [CX0001]  
M93C76(08bit)@MSOP8 [CX1015]  
M93C76(08bit)@TSSOP8 [CX1059]  
M93C76(16bit)@MLP8 [CX4001]  
M93C76(16bit)@SOIC8 [CX1045]  
M93C76R(08bit) [CX0001]  
M93C76R(08bit)@MSOP8 [CX1015]  
M93C76R(08bit)@TSSOP8 [CX1059]  
M93C76R(16bit)@MLP8 [CX4001]  
M93C76R(16bit)@SOIC8 [CX1045]  
M93C76W(08bit) [CX0001]  
M93C76W(08bit)@MSOP8 [CX1015]  
M93C76W(08bit)@TSSOP8 [CX1059]  
M93C76W(16bit)@MLP8 [CX4001]  
M93C76W(16bit)@SOIC8 [CX1045]  
M93C86(08bit) [CX0001]  
M93C86(08bit)@MSOP8 [CX1015]  
M93C86(08bit)@TSSOP8 [CX1059]  
M93C86(16bit)@MLP8 [CX4001]  
M93C86(16bit)@SOIC8 [CX1045]  
M93C86R(08bit) [CX0001]  
M93C86R(08bit)@MSOP8 [CX1015]  
M93C86R(08bit)@TSSOP8 [CX1059]  
M93C86R(16bit)@MLP8 [CX4001]  
M93C86R(16bit)@SOIC8 [CX1045]  
M93C86W(08bit) [CX0001]  
M93C86W(08bit)@MSOP8 [CX1015]  
M93C86W(08bit)@TSSOP8 [CX1059]  
M93C86W(16bit)@MLP8 [CX4001]

M93C56(08bit)@MLP8 [CX4001]  
M93C56(08bit)@SOIC8 [CX1045]  
M93C56(16bit) [CX0001]  
M93C56(16bit)@MSOP8 [CX1015]  
M93C56(16bit)@TSSOP8 [CX1059]  
M93C56R(08bit)@MLP8 [CX4001]  
M93C56R(08bit)@SOIC8 [CX1045]  
M93C56R(16bit) [CX0001]  
M93C56R(16bit)@MSOP8 [CX1015]  
M93C56R(16bit)@TSSOP8 [CX1059]  
M93C56W(08bit)@MLP8 [CX4001]  
M93C56W(08bit)@SOIC8 [CX1045]  
M93C56W(16bit) [CX0001]  
M93C56W(16bit)@MSOP8 [CX1015]  
M93C56W(16bit)@TSSOP8 [CX1059]  
M93C66(08bit)@MLP8 [CX4001]  
M93C66(08bit)@SOIC8 [CX1045]  
M93C66(16bit) [CX0001]  
M93C66(16bit)@MSOP8 [CX1015]  
M93C66(16bit)@TSSOP8 [CX1059]  
M93C66R(08bit)@MLP8 [CX4001]  
M93C66R(08bit)@SOIC8 [CX1045]  
M93C66R(16bit) [CX0001]  
M93C66R(16bit)@MSOP8 [CX1015]  
M93C66R(16bit)@TSSOP8 [CX1059]  
M93C66W(08bit)@MLP8 [CX4001]  
M93C66W(08bit)@SOIC8 [CX1045]  
M93C66W(16bit) [CX0001]  
M93C66W(16bit)@MSOP8 [CX1015]  
M93C66W(16bit)@TSSOP8 [CX1059]  
M93C76(08bit)@MLP8 [CX4001]  
M93C76(08bit)@SOIC8 [CX1045]  
M93C76(16bit) [CX0001]  
M93C76(16bit)@MSOP8 [CX1015]  
M93C76(16bit)@TSSOP8 [CX1059]  
M93C76R(08bit)@MLP8 [CX4001]  
M93C76R(08bit)@SOIC8 [CX1045]  
M93C76R(16bit) [CX0001]  
M93C76R(16bit)@MSOP8 [CX1015]  
M93C76R(16bit)@TSSOP8 [CX1059]  
M93C76W(08bit)@MLP8 [CX4001]  
M93C76W(08bit)@SOIC8 [CX1045]  
M93C76W(16bit) [CX0001]  
M93C76W(16bit)@MSOP8 [CX1015]  
M93C76W(16bit)@TSSOP8 [CX1059]  
M93C86(08bit)@MLP8 [CX4001]  
M93C86(08bit)@SOIC8 [CX1045]  
M93C86(16bit) [CX0001]  
M93C86(16bit)@MSOP8 [CX1015]  
M93C86(16bit)@TSSOP8 [CX1059]  
M93C86R(08bit)@MLP8 [CX4001]  
M93C86R(08bit)@SOIC8 [CX1045]  
M93C86R(16bit) [CX0001]  
M93C86R(16bit)@MSOP8 [CX1015]  
M93C86R(16bit)@TSSOP8 [CX1059]  
M93C86W(08bit)@MLP8 [CX4001]  
M93C86W(08bit)@SOIC8 [CX1045]  
M93C86W(16bit) [CX0001]  
M93C86W(16bit)@MSOP8 [CX1015]

M93C86W(16bit)@SOIC8 [CX1045]  
M93CS566 [CX0001]  
M93S46 [CX0001]  
M93S46@TSSOP8 [CX1059]  
M93S46R@SOIC8 [CX1045]  
M93S46W [CX0001]  
M93S46W@TSSOP8 [CX1059]  
M93S56@SOIC8 [CX1045]  
M93S56R [CX0001]  
M93S56R@TSSOP8 [CX1059]  
M93S56W@SOIC8 [CX1045]  
M93S66 [CX0001]  
M93S66@TSSOP8 [CX1059]  
M93S66R@SOIC8 [CX1045]  
M93S66W [CX0001]  
M93S66W@TSSOP8 [CX1059]  
M95010(ISP) [CX0001]  
M95010@SOIC8(ISP) [CX0001]  
M95010@TSSOP8(ISP) [CX0001]  
M95020(ISP) [CX0001]  
M95020@SOIC8(ISP) [CX1016]  
M95020@TSSOP8(ISP) [CX1059]  
M95040(ISP) [CX0001]  
M95040@SOIC8(ISP) [CX1016]  
M95040@TSSOP8(ISP) [CX1059]  
M95080(ISP) [CX0001]  
M95080@SOIC8(ISP) [CX0001]  
M95080@TSSOP14(ISP) [CX0001]  
M95080@TSSOP8(ISP) [CX0001]  
M95128(ISP)  
M95128@TSSOP14(ISP)  
M95128@TSSOP8(ISP)  
M95128[150mil]@SOIC8 [CX1045]  
M95128[200mil]@SOIC8 [CX1032]  
M95160 [CX0001]  
M95160@SOIC8 [CX1045]  
M95160@TSSOP14 [CX1000]  
M95160@TSSOP8 [CX1059]  
M95256 [CX0001]  
M95256@TSSOP14 [CX1000]  
M95256@TSSOP8 [CX1059]  
M95256@UFDFPN8 [CX4002]  
M95256[150mil]@SOIC8(ISP)  
M95256[200mil]@SOIC8(ISP)  
M95320(ISP) [CX0001]  
M95320@SOIC8(ISP) [CX0001]  
M95320@TSSOP14(ISP) [CX0001]  
M95320@TSSOP8(ISP) [CX0001]  
M95512@SOIC8 [CX1045]  
M95512@TSSOP8 [CX1059]  
M95640 [CX0001]  
M95640@SOIC8 [CX1045]  
M95640@TSSOP14 [CX1000]  
M95640@TSSOP8 [CX1059]  
M95M01-R@SOP8(150mil) [CX1045#1]  
M95M01-R@WLCS8 [CX0001]  
M95M01-W@SOP8(200mil) [CX1044#1]  
M95M02-DR@SOP8(150mil) [CX1045#1]  
M95M02-DR@SOP8(200mil) [CX1044#1]

M93C86W(16bit)@TSSOP8 [CX1059]  
M93CS566@SOIC8 [CX1045]  
M93S46@SOIC8 [CX1045]  
M93S46R [CX0001]  
M93S46R@TSSOP8 [CX1059]  
M93S46W@SOIC8 [CX1045]  
M93S56 [CX0001]  
M93S56@TSSOP8 [CX1059]  
M93S56R@SOIC8 [CX1045]  
M93S56W [CX0001]  
M93S56W@TSSOP8 [CX1059]  
M93S66@SOIC8 [CX1045]  
M93S66R [CX0001]  
M93S66R@TSSOP8 [CX1059]  
M93S66W@SOIC8 [CX1045]  
M95010 [CX0001]  
M95010@SOIC8 [CX1045]  
M95010@TSSOP8 [CX1059]  
M95020 [CX0001]  
M95020@SOIC8 [CX1045]  
M95020@TSSOP8 [CX1059]  
M95040 [CX0001]  
M95040@SOIC8 [CX1045]  
M95040@TSSOP8 [CX1059]  
M95080 [CX0001]  
M95080@SOIC8 [CX1045]  
M95080@TSSOP14 [CX1000]  
M95080@TSSOP8 [CX1059]  
M95128 [CX0001]  
M95128@TSSOP14 [CX1000]  
M95128@TSSOP8 [CX1059]  
M95128@UFDFPN8 [CX4002]  
M95128[150mil]@SOIC8(ISP)  
M95128[200mil]@SOIC8(ISP)  
M95160(ISP) [CX0001]  
M95160@SOIC8(ISP) [CX0001]  
M95160@TSSOP14(ISP) [CX0001]  
M95160@TSSOP8(ISP) [CX0001]  
M95256(ISP)  
M95256@TSSOP14(ISP)  
M95256@TSSOP8(ISP)  
M95256[150mil]@SOIC8 [CX1045]  
M95256[200mil]@SOIC8 [CX1032]  
M95320 [CX0001]  
M95320@SOIC8 [CX1045]  
M95320@TSSOP14 [CX1000]  
M95320@TSSOP8 [CX1059]  
M95320@UFDFPN8 [CX4002]  
M95512@SOIC8(ISP)  
M95512@TSSOP8(ISP)  
M95640(ISP) [CX0001]  
M95640@SOIC8(ISP) [CX0001]  
M95640@TSSOP14(ISP) [CX0001]  
M95640@TSSOP8(ISP) [CX0001]  
M95M01-R@SOP8(200mil) [CX1044#1]  
M95M01-W@SOP8(150mil) [CX1045#1]  
M95M01-W@WLCS8 [CX0001]

M95M02-DR@WLCS8 [CX0001]  
M95P02@SOIC8 [CX1045]  
M95P04@SOIC8 [CX1045]  
M95P08@SOIC8 [CX1045]  
MK48C02B [CX0001]  
MK48C12B [CX0001]  
MK48T02B [CX0001]  
MK48T12 [CX0001]  
MK48T18 [CX0001]  
MK48T32Y [CX0001]  
MK48T35@SOIC28 [CX1033]  
MK48T35Y@SOIC28 [CX1033]  
MK48T512Y [CX0001]  
MK48Z02B [CX0001]  
MK48Z12 [CX0001]  
MK48Z18 [CX0001]  
MK48Z32Y [CX0001]  
MK48Z35@SOIC28 [CX1033]  
MK48Z35Y@SOIC28 [CX1033]  
MK48Z512Y [CX0001]  
MKI48Z02B [CX0001]  
MKI48Z12B [CX0001]  
N29L064@FBGA48 [CX5157]  
N29L064@TSOP48 [CX0001]  
N29Q064@BGA48 [CX5157]  
NAND01GW3A0AN6@TSOP48 [CX1004]  
NAND01GW3B2BN6@TSOP48 [CX1004]  
NAND02GW3B2AN6@TSOP48 [CX1004]  
NAND02GW3B2DN6@TSOP48 [CX1004]  
NAND04GW3B2DN6@TSOP48 [CX1004-1]  
NAND08GW3B2AN6@TSOP48 [CX1004-3]  
NAND08GW3F2AN6@TSOP48 [CX1004-1]  
NAND128W3A2BN6@TSOP48 [CX1004]  
NAND256W3A0AN6@TSOP48 [CX1004]  
NAND512W3A0AN6@TSOP48 [CX1004]  
NAND512W3A2CN6@TSOP48 [CX1004]  
NAND512W3A2SN6@TSOP48 [CX1004]  
ST24C01@SOIC8 [CX1045]  
ST24C02A@SOIC8 [CX1045]  
ST24C16@SOIC8  
ST24FC21@SOIC8 [CX1045]  
ST24FW21@SOIC8 [CX1045]  
ST24LC21B@SOIC8 [CX1045]  
ST24LW21@SOIC8 [CX1045]  
ST24W01@SOIC8  
ST24W02@SOIC8  
ST24W04C@SOIC8  
ST26C201@PLCC32 [CX2032]  
ST27128A [CX0001]  
ST2764A [CX0001]  
ST93C06(08bit) [CX0001]  
ST93C06(16bit) [CX0001]  
ST93C46(08bit) [CX0001]  
ST93C46(16bit) [CX0001]  
ST93C46A(08bit) [CX0001]  
ST93C46A(16bit) [CX0001]  
ST93C46C(08bit) [CX0001]  
ST93C46C(16bit) [CX0001]  
ST93C46T(08bit) [CX0001]  
M95P02 [CX0001]  
M95P04 [CX0001]  
M95P08 [CX0001]  
MK48C02 [CX0001]  
MK48C12 [CX0001]  
MK48T02 [CX0001]  
MK48T08 [CX0001]  
MK48T12B [CX0001]  
MK48T32 [CX0001]  
MK48T35 [CX0001]  
MK48T35Y [CX0001]  
MK48T512V [CX0001]  
MK48Z02 [CX0001]  
MK48Z08 [CX0001]  
MK48Z12B [CX0001]  
MK48Z32 [CX0001]  
MK48Z35 [CX0001]  
MK48Z35Y [CX0001]  
MK48Z512V [CX0001]  
MKI48Z02 [CX0001]  
MKI48Z12 [CX0001]  
MKI48Z18 [CX0001]  
N29L064@PSOP44 [CX0001]  
N29Q064#PSOP44 [CX0001]  
N29Q064@TSOP48 [CX0001]  
NAND01GW3B2AN6@TSOP48 [CX1004]  
NAND01GW3B2CN6@TSOP48 [CX1004-1]  
NAND02GW3B2CN6@TSOP48 [CX1004]  
NAND04GW3B2BN6@TSOP48 [CX1004]  
NAND04GW3C2BN6@TSOP48 [CX1004]  
NAND08GW3B2CN6@TSOP48 [CX1004-3]  
NAND128W3A0AN6@TSOP48 [CX1004]  
NAND16GW3C4AN1@TSOP48 [CX1004]  
NAND256W3A2BN6@TSOP48 [CX1004]  
NAND512W3A2BN6@TSOP48 [CX1004]  
NAND512W3A2DN6@TSOP48 [CX1004]  
ST24C01 [CX0001]  
ST24C02A [CX0001]  
ST24C16 [CX0001]  
ST24FC21 [CX0001]  
ST24FW21 [CX0001]  
ST24LC21B [CX0001]  
ST24LW21 [CX0001]  
ST24W01 [CX0001]  
ST24W02 [CX0001]  
ST24W04C [CX0001]  
ST26C201 [CX0001]  
ST26C201@TSOP32 [CX1002]  
ST27256 [CX0001]  
ST27C256 [CX0001]  
ST93C06(08bit)@SOIC8 [CX1045]  
ST93C06(16bit)@SOIC8 [CX1045]  
ST93C46(08bit)@SOIC8 [CX1045]  
ST93C46(16bit)@SOIC8 [CX1045]  
ST93C46A(08bit)@SOIC8 [CX1045]  
ST93C46A(16bit)@SOIC8 [CX1045]  
ST93C46C(08bit)@SOIC8 [CX1045]  
ST93C46C(16bit)@SOIC8 [CX1045]  
ST93C46T(08bit)@SOIC8 [CX1045]



ST93C46T(16bit) [CX0001]	ST93C46T(16bit)@SOIC8 [CX1045]
ST93C47C(08bit) [CX0001]	ST93C47C(08bit)@SOIC8 [CX1045]
ST93C47C(16bit) [CX0001]	ST93C47C(16bit)@SOIC8 [CX1045]
ST93C47T(08bit) [CX0001]	ST93C47T(08bit)@SOIC8 [CX1045]
ST93C47T(16bit) [CX0001]	ST93C47T(16bit)@SOIC8 [CX1045]
ST93C56(08bit) [CX0001]	ST93C56(08bit)@SOIC8 [CX1045]
ST93C56(16bit) [CX0001]	ST93C56(16bit)@SOIC8 [CX1045]
ST93C56B(08bit) [CX0001]	ST93C56B(08bit)@SOIC8 [CX1045]
ST93C56B(16bit) [CX0001]	ST93C56B(16bit)@SOIC8 [CX1045]
ST93C56C(08bit) [CX0001]	ST93C56C(08bit)@SOIC8 [CX1045]
ST93C56C(16bit) [CX0001]	ST93C56C(16bit)@SOIC8 [CX1045]
ST93C57C(08bit) [CX0001]	ST93C57C(08bit)@SOIC8 [CX1045]
ST93C57C(16bit) [CX0001]	ST93C57C(16bit)@SOIC8 [CX1045]
ST93C66(08bit) [CX0001]	ST93C66(08bit)@SOIC8 [CX1045]
ST93C66(16bit) [CX0001]	ST93C66(16bit)@SOIC8 [CX1045]
ST93C67(08bit) [CX0001]	ST93C67(08bit)@SOIC8 [CX1045]
ST93C67(16bit) [CX0001]	ST93C67(16bit)@SOIC8 [CX1045]
ST93C76(08bit) [CX0001]	ST93C76(08bit)@SOIC8 [CX1045]
ST93C76(16bit) [CX0001]	ST93C76(16bit)@SOIC8 [CX1045]
ST93C86(08bit) [CX0001]	ST93C86(08bit)@SOIC8 [CX1045]
ST93C86(16bit) [CX0001]	ST93C86(16bit)@SOIC8 [CX1045]
ST93CS46 [CX0001]	ST93CS46@SOIC8 [CX1045]
ST93CS47 [CX0001]	ST93CS47@SOIC8 [CX1045]
ST93CS56 [CX0001]	ST93CS56@SOIC8 [CX1045]
ST93CS566 [CX0001]	ST93CS566@SOIC8 [CX1045]
ST93CS57 [CX0001]	ST93CS57@SOIC8 [CX1045]
ST93CS66 [CX0001]	ST93CS66@SOIC14 [CX1016]
ST93CS67 [CX0001]	ST93CS67@SOIC14 [CX1016]
STTS2002@TDFN8 [CX4002]	TS27C256 [CX0001]
TS27C64 [CX0001]	TS27C64@PLCC32 [CX2032]
TS27C64A [CX0001]	TS27C64A@PLCC32 [CX2032]
TS28C16A [CX0001]	TS28C17A [CX0001]

## MICROCONTROLLER

IST7FLITE02B6 [CX0001]	IST7FLITE05B6 [CX0001]
IST7FLITE09B6 [CX0001]	IST7FLITES2B6 [CX0001]
IST7FLITES5B6 [CX0001]	PSD211R@PLCC44 [CX2044]
PSD211R@TQFP44 [CX3003]	PSD301@PLCC44 [CX2044]
PSD301@TQFP44 [CX3003]	PSD301B@PLCC44 [CX2044]
PSD301L@PLCC44 [CX2044]	PSD301L@TQFP44 [CX3003]
PSD301R@PLCC44 [CX2044]	PSD301R@TQFP44 [CX3003]
PSD301RV@PLCC44 [CX2044]	PSD301V@PLCC44 [CX2044]
PSD302@PLCC44 [CX2044]	PSD302@TQFP44 [CX3003]
PSD302B@PLCC44 [CX2044]	PSD302B@PLCC44(USA) [CX2044]
PSD302L@PLCC44 [CX2044]	PSD302L@TQFP44 [CX3003]
PSD302R@PLCC44 [CX2044]	PSD302R@TQFP44 [CX3003]
PSD302RV@PLCC44 [CX2044]	PSD302V@PLCC44 [CX2044]
PSD303@PLCC44 [CX2044]	PSD303@TQFP44 [CX3003]
PSD303L@PLCC44 [CX2044]	PSD303L@TQFP44 [CX3003]
PSD303R@PLCC44 [CX2044]	PSD303R@TQFP44 [CX3003]
PSD303RV@PLCC44 [CX2044]	PSD303V@PLCC44 [CX2044]
PSD311@PLCC44 [CX2044]	PSD311@TQFP44 [CX3003]
PSD311B@PLCC44 [CX2044]	PSD311L@PLCC44 [CX2044]
PSD311L@TQFP44 [CX3003]	PSD311R@PLCC44 [CX2044]
PSD311R@TQFP44 [CX3003]	PSD311RV@PLCC44 [CX2044]
PSD311V@PLCC44 [CX2044]	PSD312@PLCC44 [CX2044]
PSD312@TQFP44 [CX3046]	PSD312B@PLCC44 [CX2044]
PSD312L@PLCC44 [CX2044]	PSD312L@TQFP44 [CX3046]

PSD312R@PLCC44 [CX2044]  
PSD312RV@PLCC44 [CX2044]  
PSD313@PLCC44 [CX2044]  
PSD313-B@PLCC44 [CX2044]  
PSD313L@PLCC44 [CX2044]  
PSD313R@PLCC44 [CX2044]  
PSD313RV@PLCC44 [CX2044]  
ST62E01 [CX0001]  
ST62E01CF1 [CX0001]  
ST62E20@SOIC20 [CX1033]  
ST62E25 [CX1033]  
ST62E25CF1 [CX0001]  
ST62T00 [CX0001]  
ST62T00C(B6) [CX0001]  
ST62T00C(N6)@SSOP16 [CX1026]  
ST62T01@SOIC16 [CX1033]  
ST62T01C(B6) [CX0001]  
ST62T01C(M6)@SOIC16 [CX1033]  
ST62T01C(N6)@SSOP16 [CX1026]  
ST62T03@SOIC16 [CX1033]  
ST62T03C(M3)@SOIC16 [CX1033]  
ST62T03C(N6)@SSOP16 [CX1026]  
ST62T08@SOIC20 [CX1033]  
ST62T08C(M6)@SOIC20 [CX1033]  
ST62T09@SOIC20 [CX1033]  
ST62T09C(B6) [CX0001]  
ST62T09C(M6)@SOIC20 [CX1033]  
ST62T10@SOIC20 [CX1033]  
ST62T10C(M6)@SOIC20 [CX1033]  
ST62T15@SOIC28 [CX1033]  
ST62T15C(M6)@SOIC28 [CX1033]  
ST62T20@SOIC20 [CX1033]  
ST62T20C(B6) [CX0001]  
ST62T20C(M6)@SOIC20 [CX1033]  
ST62T25@SOIC28 [CX1033]  
ST62T25C(B6) [CX0001]  
ST62T25C(M6)@SOIC28 [CX1033]  
ST62T65C(B3) [CX0001]  
ST62T65C(M3)@SOIC28 [CX1033]  
ST62T65C(N6)@SSOP28 [CX1026]  
ST72F260G1M6@SOIC28 [CX1033]  
ST72F260G2H1@LFBGA36 [CX5063]  
ST72F260G2M6@SOIC28 [CX1033]  
ST72F262G1M6@SOIC28 [CX1033]  
ST72F262G2H1@LFBGA36 [CX5063]  
ST72F262G2M6@SOIC28 [CX1033]  
ST72F264G1M6@SOIC28 [CX1033]  
ST72F264G2H1@LFBGA36 [CX5063]  
ST72F264G2M6@SOIC28 [CX1033]  
ST72F321AR6T6@TQFP64 [CX3011]  
ST72F321AR7T3@TQFP64 [CX3011]  
ST72F321AR7TA@TQFP64 [CX3011]  
ST72F321AR9T6@TQFP64 [CX3011]  
ST72F321AR9TC@TQFP64 [CX3011]  
ST72F321BAR6T6@TQFP64 [CX3011]  
ST72F321BAR7T3@TQFP64 [CX3011]  
ST72F321BAR7TA@TQFP64 [CX3011]  
ST72F321BAR9T6@TQFP64 [CX3011]  
ST72F321BAR9TC@TQFP64 [CX3011]

PSD312R@TQFP44 [CX3046]  
PSD312V@PLCC44 [CX2044]  
PSD313@TQFP44 [CX3003]  
PSD313-B@TQFP44 [CX3003]  
PSD313L@TQFP44 [CX3003]  
PSD313R@TQFP44 [CX3003]  
PSD313V@PLCC44 [CX2044]  
ST62E01@SOIC16 [CX1033]  
ST62E20 [CX0001]  
ST62E20CF1 [CX0001]  
ST62E25@SOIC28 [CX1033]  
ST62E65CF1 [CX0001]  
ST62T00@SOIC16 [CX1033]  
ST62T00C(M6)@SOIC16 [CX1033]  
ST62T01 [CX0001]  
ST62T01C(B3) [CX0001]  
ST62T01C(M3)@SOIC16 [CX1033]  
ST62T01C(N3)@SSOP16 [CX1026]  
ST62T03 [CX0001]  
ST62T03C(B6) [CX0001]  
ST62T03C(M6)@SOIC16 [CX1033]  
ST62T08 [CX0001]  
ST62T08C(B6) [CX0001]  
ST62T09 [CX0001]  
ST62T09C(B3) [CX0001]  
ST62T09C(M3)@SOIC20 [CX1033]  
ST62T10 [CX0001]  
ST62T10C(B6) [CX0001]  
ST62T15 [CX0001]  
ST62T15C(B6) [CX0001]  
ST62T20 [CX0001]  
ST62T20C(B3) [CX0001]  
ST62T20C(M3)@SOIC20 [CX1033]  
ST62T25 [CX0001]  
ST62T25C(B3) [CX0001]  
ST62T25C(M3)@SOIC28 [CX1033]  
ST62T25C(N6)@SSOP28 [CX1026]  
ST62T65C(B6) [CX0001]  
ST62T65C(M6)@SOIC28 [CX1033]  
ST72F260G1B6@SDIP32 [CX0032]  
ST72F260G2B6@SDIP32 [CX0032]  
ST72F260G2H6@LFBGA36 [CX5063]  
ST72F262G1B6@SDIP32 [CX0032]  
ST72F262G2B6@SDIP32 [CX0032]  
ST72F262G2H6@LFBGA36 [CX5063]  
ST72F264G1B6@SDIP32 [CX0032]  
ST72F264G2B6@SDIP32 [CX0032]  
ST72F264G2H6@LFBGA36 [CX5063]  
ST72F321AR6T3@TQFP64 [CX3011]  
ST72F321AR6TA@TQFP64 [CX3011]  
ST72F321AR7T6@TQFP64 [CX3011]  
ST72F321AR9T3@TQFP64 [CX3011]  
ST72F321AR9TA@TQFP64 [CX3011]  
ST72F321BAR6T3@TQFP64 [CX3011]  
ST72F321BAR6TA@TQFP64 [CX3011]  
ST72F321BAR7T6@TQFP64 [CX3011]  
ST72F321BAR9T3@TQFP64 [CX3011]  
ST72F321BAR9TA@TQFP64 [CX3011]  
ST72F321BJ6T3@TQFP44 [CX3003]

ST72F321BJ6T6@TQFP44 [CX3003] ST72F321BJ6TA@TQFP44 [CX3003]  
ST72F321BJ7T3@TQFP44 [CX3003] ST72F321BJ7T6@TQFP44 [CX3003]  
ST72F321BJ7TA@TQFP44 [CX3003] ST72F321BJ9T3@TQFP44 [CX3003]  
ST72F321BJ9T6@TQFP44 [CX3003] ST72F321BJ9TA@TQFP44 [CX3003]  
ST72F321BJ9TC@TQFP44 [CX3003] ST72F321BM9T3@TQFP80 [CX3054]  
ST72F321BM9T6@TQFP80 [CX3054] ST72F321BM9TC@TQFP80 [CX3054]  
ST72F321BR6T3@TQFP64 [CX3013] ST72F321BR6T6@TQFP64 [CX3013]  
ST72F321BR6TA@TQFP64 [CX3013] ST72F321BR7T3@TQFP64 [CX3013]  
ST72F321BR7T6@TQFP64 [CX3013] ST72F321BR7TA@TQFP64 [CX3013]  
ST72F321BR9T3@TQFP64 [CX3013] ST72F321BR9T6@TQFP64 [CX3013]  
ST72F321BR9TA@TQFP64 [CX3013] ST72F321BR9TC@TQFP64 [CX3013]  
ST72F321J6T3@TQFP44 [CX3003] ST72F321J6T6@TQFP44 [CX3003]  
ST72F321J6TA@TQFP44 [CX3003] ST72F321J7T3@TQFP44 [CX3003]  
ST72F321J7T6@TQFP44 [CX3003] ST72F321J7TA@TQFP44 [CX3003]  
ST72F321J9T3@TQFP44 [CX3003] ST72F321J9T6@TQFP44 [CX3003]  
ST72F321J9TA@TQFP44 [CX3003] ST72F321J9TC@TQFP44 [CX3003]  
ST72F321M9T3@TQFP80 [CX3054] ST72F321M9T6@TQFP80 [CX3054]  
ST72F321M9TC@TQFP80 [CX3054] ST72F321R6T3@TQFP64 [CX3013]  
ST72F321R6T6@TQFP64 [CX3013] ST72F321R6TA@TQFP64 [CX3013]  
ST72F321R7T3@TQFP64 [CX3013] ST72F321R7T6@TQFP64 [CX3013]  
ST72F321R7TA@TQFP64 [CX3013] ST72F321R9T3@TQFP64 [CX3013]  
ST72F321R9T6@TQFP64 [CX3013] ST72F321R9TA@TQFP64 [CX3013]  
ST72F321R9TC@TQFP64 [CX3013] ST72F324BJ2B3@SDIP42 [CX0042]  
ST72F324BJ2B5@SDIP42 [CX0042] ST72F324BJ2B5@SDIP42(new) [CX0042]  
ST72F324BJ2B6@SDIP42 [CX0042] ST72F324BJ2B6@SDIP42(new) [CX0042]  
ST72F324BJ2BA@SDIP42 [CX0042] ST72F324BJ2BA@SDIP42(new) [CX0042]  
ST72F324BJ2BC@SDIP42 [CX0042] ST72F324BJ2BC@SDIP42(new) [CX0042]  
ST72F324BJ2T3@TQFP44 [CX3003] ST72F324BJ2T3@TQFP44(new) [CX3003]  
ST72F324BJ2T5@TQFP44 [CX3003] ST72F324BJ2T5@TQFP44(new) [CX3003]  
ST72F324BJ2T6@TQFP44 [CX3003] ST72F324BJ2T6@TQFP44(new) [CX3003]  
ST72F324BJ2TA@TQFP44 [CX3003] ST72F324BJ2TA@TQFP44(new) [CX3003]  
ST72F324BJ2TC@TQFP44 [CX3003] ST72F324BJ2TC@TQFP44(new) [CX3003]  
ST72F324BJ4B3@SDIP42 [CX0042] ST72F324BJ4B3@SDIP42(new) [CX0042]  
ST72F324BJ4B5@SDIP42 [CX0042] ST72F324BJ4B5@SDIP42(new) [CX0042]  
ST72F324BJ4B6@SDIP42 [CX0042] ST72F324BJ4B6@SDIP42(new) [CX0042]  
ST72F324BJ4BA@SDIP42 [CX0042] ST72F324BJ4BA@SDIP42(new) [CX0042]  
ST72F324BJ4BC@SDIP42 [CX0042] ST72F324BJ4BC@SDIP42(new) [CX0042]  
ST72F324BJ4T3@TQFP44 [CX3003] ST72F324BJ4T3@TQFP44(new) [CX3003]  
ST72F324BJ4T5@TQFP44 [CX3003] ST72F324BJ4T5@TQFP44(new) [CX3003]  
ST72F324BJ4T6@TQFP44 [CX3003] ST72F324BJ4T6@TQFP44(new) [CX3003]  
ST72F324BJ4TA@TQFP44 [CX3003]

ST72F324BJ4TA@TQFP44(new) [CX3003]  
ST72F324BJ4TC@TQFP44 [CX3003]  
ST72F324BJ4TC@TQFP44(new) [CX3003]  
ST72F324BJ6B3@SDIP42 [CX0042]  
ST72F324BJ6B3@SDIP42(new) [CX0042]  
ST72F324BJ6B5@SDIP42 [CX0042]  
ST72F324BJ6B5@SDIP42(new) [CX0042]  
ST72F324BJ6B6@SDIP42 [CX0042]  
ST72F324BJ6B6@SDIP42(new) [CX0042]  
ST72F324BJ6BA@SDIP42 [CX0042]  
ST72F324BJ6BA@SDIP42(new) [CX0042]  
ST72F324BJ6BC@SDIP42 [CX0042]  
ST72F324BJ6BC@SDIP42(new) [CX0042]  
ST72F324BJ6T3@TQFP44 [CX3003]  
ST72F324BJ6T3@TQFP44(new) [CX3003]  
ST72F324BJ6T5@TQFP44 [CX3003]  
ST72F324BJ6T5@TQFP44(new) [CX3003]  
ST72F324BJ6T6@TQFP44 [CX3003]  
ST72F324BJ6T6@TQFP44(new) [CX3003]  
ST72F324BJ6TA@TQFP44 [CX3003]  
ST72F324BJ6TA@TQFP44(new) [CX3003]  
ST72F324BJ6TC@TQFP44 [CX3003]  
ST72F324BJ6TC@TQFP44(new) [CX3003]  
ST72F324BK2B3@SDIP32 [CX0032]  
ST72F324BK2B3@SDIP32(new) [CX0032]  
ST72F324BK2B5@SDIP32 [CX0032]  
ST72F324BK2B5@SDIP32(new) [CX0032]  
ST72F324BK2B6@SDIP32 [CX0032]  
ST72F324BK2B6@SDIP32(new) [CX0032]  
ST72F324BK2BA@SDIP32 [CX0032]  
ST72F324BK2BA@SDIP32(new) [CX0032]  
ST72F324BK2BC@SDIP32 [CX0032]  
ST72F324BK2BC@SDIP32(new) [CX0032]  
ST72F324BK2T3@TQFP32 [CX3001]  
ST72F324BK2T3@TQFP32(new) [CX3001]  
ST72F324BK2T5@TQFP32 [CX3001]  
ST72F324BK2T5@TQFP32(new) [CX3001]  
ST72F324BK2T6@TQFP32 [CX3001]  
ST72F324BK2T6@TQFP32(new) [CX3001]  
ST72F324BK2TA@TQFP32 [CX3001]  
ST72F324BK2TA@TQFP32(new) [CX3001]  
ST72F324BK2TC@TQFP32 [CX3001]  
ST72F324BK2TC@TQFP32(new) [CX3001]  
ST72F324BK4B3@SDIP32 [CX0032]  
ST72F324BK4B3@SDIP32(new) [CX0032]  
ST72F324BK4B5@SDIP32 [CX0032]  
ST72F324BK4B5@SDIP32(new) [CX0032]  
ST72F324BK4B6@SDIP32 [CX0032]  
ST72F324BK4B6@SDIP32(new) [CX0032]  
ST72F324BK4BA@SDIP32 [CX0032]  
ST72F324BK4BA@SDIP32(new) [CX0032]  
ST72F324BK4BC@SDIP32 [CX0032]  
ST72F324BK4BC@SDIP32(new) [CX0032]  
ST72F324BK4T3@TQFP32 [CX3001]  
ST72F324BK4T3@TQFP32(new) [CX3001]  
ST72F324BK4T5@TQFP32 [CX3001]  
ST72F324BK4T5@TQFP32(new) [CX3001]  
ST72F324BK4T6@TQFP32 [CX3001]  
ST72F324BK4T6@TQFP32(new) [CX3001]

ST72F324BK4TA@TQFP32 [CX3001]  
ST72F324BK4TA@TQFP32(new) [CX3001]  
ST72F324BK4TC@TQFP32 [CX3001]  
ST72F324BK4TC@TQFP32(new) [CX3001]  
ST72F324BK6B3@SDIP32 [CX0032]  
ST72F324BK6B3@SDIP32(new) [CX0032]  
ST72F324BK6B5@SDIP32 [CX0032]  
ST72F324BK6B5@SDIP32(new) [CX0032]  
ST72F324BK6B6@SDIP32 [CX0032]  
ST72F324BK6B6@SDIP32(new) [CX0032]  
ST72F324BK6BA@SDIP32 [CX0032]  
ST72F324BK6BA@SDIP32(new) [CX0032]  
ST72F324BK6BC@SDIP32 [CX0032]  
ST72F324BK6BC@SDIP32(new) [CX0032]  
ST72F324BK6T3@TQFP32 [CX3001]  
ST72F324BK6T3@TQFP32(new) [CX3001]  
ST72F324BK6T5@TQFP32 [CX3001]  
ST72F324BK6T5@TQFP32(new) [CX3001]  
ST72F324BK6T6@TQFP32 [CX3001]  
ST72F324BK6T6@TQFP32(new) [CX3001]  
ST72F324BK6TA@TQFP32 [CX3001]  
ST72F324BK6TA@TQFP32(new) [CX3001]  
ST72F324BK6TC@TQFP32 [CX3001]  
ST72F324BK6TC@TQFP32(new) [CX3001]  
ST72F324J2B3@SDIP42 [CX0042]  
ST72F324J2B3@SDIP42(new) [CX0042]  
ST72F324J2B5@SDIP42 [CX0042]  
ST72F324J2B5@SDIP42(new) [CX0042]  
ST72F324J2B6@SDIP42 [CX0042]  
ST72F324J2B6@SDIP42(new) [CX0042]  
ST72F324J2BA@SDIP42 [CX0042]  
ST72F324J2BA@SDIP42(new) [CX0042]  
ST72F324J2BC@SDIP42 [CX0042]  
ST72F324J2BC@SDIP42(new) [CX0042]  
ST72F324J2T3@TQFP44 [CX3003]  
ST72F324J2T3@TQFP44(new) [CX3003]  
ST72F324J2T5@TQFP44 [CX3003]  
ST72F324J2T5@TQFP44(new) [CX3003]  
ST72F324J2T6@TQFP44 [CX3003]  
ST72F324J2T6@TQFP44(new) [CX3003]  
ST72F324J2TA@TQFP44 [CX3003]  
ST72F324J2TA@TQFP44(new) [CX3003]  
ST72F324J2TC@TQFP44 [CX3003]  
ST72F324J2TC@TQFP44(new) [CX3003]  
ST72F324J4B3@SDIP42 [CX0042]  
ST72F324J4B3@SDIP42(new) [CX0042]  
ST72F324J4B5@SDIP42 [CX0042]  
ST72F324J4B5@SDIP42(new) [CX0042]  
ST72F324J4B6@SDIP42 [CX0042]  
ST72F324J4B6@SDIP42(new) [CX0042]  
ST72F324J4BA@SDIP42 [CX0042]  
ST72F324J4BA@SDIP42(new) [CX0042]  
ST72F324J4BC@SDIP42 [CX0042]  
ST72F324J4BC@SDIP42(new) [CX0042]  
ST72F324J4T3@TQFP44 [CX3003]  
ST72F324J4T3@TQFP44(new) [CX3003]  
ST72F324J4T5@TQFP44 [CX3003]  
ST72F324J4T5@TQFP44(new) [CX3003]  
ST72F324J4T6@TQFP44 [CX3003]

ST72F324J4T6@TQFP44(new) [CX3003]  
ST72F324J4TA@TQFP44 [CX3003]  
ST72F324J4TA@TQFP44(new) [CX3003]  
ST72F324J4TC@TQFP44 [CX3003]  
ST72F324J4TC@TQFP44(new) [CX3003]  
ST72F324J6B3@SDIP42 [CX0042]  
ST72F324J6B3@SDIP42(new) [CX0042]  
ST72F324J6B5@SDIP42 [CX0042]  
ST72F324J6B5@SDIP42(new) [CX0042]  
ST72F324J6B6@SDIP42 [CX0042]  
ST72F324J6B6@SDIP42(new) [CX0042]  
ST72F324J6BA@SDIP42 [CX0042]  
ST72F324J6BA@SDIP42(new) [CX0042]  
ST72F324J6BC@SDIP42 [CX0042]  
ST72F324J6BC@SDIP42(new) [CX0042]  
ST72F324J6T3@TQFP44 [CX3003]  
ST72F324J6T3@TQFP44(new) [CX3003]  
ST72F324J6T5@TQFP44 [CX3003]  
ST72F324J6T5@TQFP44(new) [CX3003]  
ST72F324J6T6@TQFP44 [CX3003]  
ST72F324J6T6@TQFP44(new) [CX3003]  
ST72F324J6TA@TQFP44 [CX3003]  
ST72F324J6TA@TQFP44(new) [CX3003]  
ST72F324J6TC@TQFP44 [CX3003]  
ST72F324J6TC@TQFP44(new) [CX3003]  
ST72F324K2B3@SDIP32 [CX0032]  
ST72F324K2B3@SDIP32(new) [CX0032]  
ST72F324K2B5@SDIP32 [CX0032]  
ST72F324K2B5@SDIP32(new) [CX0032]  
ST72F324K2B6@SDIP32 [CX0032]  
ST72F324K2B6@SDIP32(new) [CX0032]  
ST72F324K2BA@SDIP32 [CX0032]  
ST72F324K2BA@SDIP32(new) [CX0032]  
ST72F324K2BC@SDIP32 [CX0032]  
ST72F324K2BC@SDIP32(new) [CX0032]  
ST72F324K2T3@TQFP32 [CX3001]  
ST72F324K2T3@TQFP32(new) [CX3001]  
ST72F324K2T5@TQFP32 [CX3001]  
ST72F324K2T5@TQFP32(new) [CX3001]  
ST72F324K2T6@TQFP32 [CX3001]  
ST72F324K2T6@TQFP32(new) [CX3001]  
ST72F324K2TA@TQFP32 [CX3001]  
ST72F324K2TA@TQFP32(new) [CX3001]  
ST72F324K2TC@TQFP32 [CX3001]  
ST72F324K2TC@TQFP32(new) [CX3001]  
ST72F324K4B3@SDIP32 [CX0032]  
ST72F324K4B3@SDIP32(new) [CX0032]  
ST72F324K4B5@SDIP32 [CX0032]  
ST72F324K4B5@SDIP32(new) [CX0032]  
ST72F324K4B6@SDIP32 [CX0032]  
ST72F324K4B6@SDIP32(new) [CX0032]  
ST72F324K4BA@SDIP32 [CX0032]  
ST72F324K4BA@SDIP32(new) [CX0032]  
ST72F324K4BC@SDIP32 [CX0032]  
ST72F324K4BC@SDIP32(new) [CX0032]  
ST72F324K4T3@TQFP32 [CX3001]  
ST72F324K4T3@TQFP32(new) [CX3001]  
ST72F324K4T5@TQFP32 [CX3001]  
ST72F324K4T5@TQFP32(new) [CX3001]

ST72F324K4T6@TQFP32 [CX3001]  
ST72F324K4T6@TQFP32(new) [CX3001]  
ST72F324K4TA@TQFP32 [CX3001]  
ST72F324K4TA@TQFP32(new) [CX3001]  
ST72F324K4TC@TQFP32 [CX3001]  
ST72F324K4TC@TQFP32(new) [CX3001]  
ST72F324K6B3@SDIP32 [CX0032]  
ST72F324K6B3@SDIP32(new) [CX0032]  
ST72F324K6B5@SDIP32 [CX0032]  
ST72F324K6B5@SDIP32(new) [CX0032]  
ST72F324K6B6@SDIP32 [CX0032]  
ST72F324K6B6@SDIP32(new) [CX0032]  
ST72F324K6BA@SDIP32 [CX0032]  
ST72F324K6BA@SDIP32(new) [CX0032]  
ST72F324K6BC@SDIP32 [CX0032]  
ST72F324K6BC@SDIP32(new) [CX0032]  
ST72F324K6T3@TQFP32 [CX3001]  
ST72F324K6T3@TQFP32(new) [CX3001]  
ST72F324K6T5@TQFP32 [CX3001]  
ST72F324K6T5@TQFP32(new) [CX3001]  
ST72F324K6T6@TQFP32 [CX3001]  
ST72F324K6T6@TQFP32(new) [CX3001]  
ST72F324K6TA@TQFP32 [CX3001]  
ST72F324K6TA@TQFP32(new) [CX3001]  
ST72F324K6TC@TQFP32 [CX3001]  
ST72F324K6TC@TQFP32(new) [CX3001]  
ST72F324LJ2B3@SDIP42 [CX0042]  
ST72F324LJ2B3@SDIP42(new) [CX0042]  
ST72F324LJ2B5@SDIP42 [CX0042]  
ST72F324LJ2B5@SDIP42(new) [CX0042]  
ST72F324LJ2B6@SDIP42 [CX0042]  
ST72F324LJ2B6@SDIP42(new) [CX0042]  
ST72F324LJ2BA@SDIP42 [CX0042]  
ST72F324LJ2BA@SDIP42(new) [CX0042]  
ST72F324LJ2BC@SDIP42 [CX0042]  
ST72F324LJ2BC@SDIP42(new) [CX0042]  
ST72F324LJ2T3@TQFP44 [CX3003]  
ST72F324LJ2T3@TQFP44(new) [CX3003]  
ST72F324LJ2T5@TQFP44 [CX3003]  
ST72F324LJ2T5@TQFP44(new) [CX3003]  
ST72F324LJ2T6@TQFP44 [CX3003]  
ST72F324LJ2T6@TQFP44(new) [CX3003]  
ST72F324LJ2TA@TQFP44 [CX3003]  
ST72F324LJ2TA@TQFP44(new) [CX3003]  
ST72F324LJ2TC@TQFP44 [CX3003]  
ST72F324LJ2TC@TQFP44(new) [CX3003]  
ST72F324LJ4B3@SDIP42 [CX0042]  
ST72F324LJ4B3@SDIP42(new) [CX0042]  
ST72F324LJ4B5@SDIP42 [CX0042]  
ST72F324LJ4B5@SDIP42(new) [CX0042]  
ST72F324LJ4B6@SDIP42 [CX0042]  
ST72F324LJ4B6@SDIP42(new) [CX0042]  
ST72F324LJ4BA@SDIP42 [CX0042]  
ST72F324LJ4BA@SDIP42(new) [CX0042]  
ST72F324LJ4BC@SDIP42 [CX0042]  
ST72F324LJ4BC@SDIP42(new) [CX0042]  
ST72F324LJ4T3@TQFP44 [CX3003]  
ST72F324LJ4T3@TQFP44(new) [CX3003]  
ST72F324LJ4T5@TQFP44 [CX3003]

ST72F324LJ4T5@TQFP44(new) [CX3003]  
ST72F324LJ4T6@TQFP44 [CX3003]  
ST72F324LJ4T6@TQFP44(new) [CX3003]  
ST72F324LJ4TA@TQFP44 [CX3003]  
ST72F324LJ4TA@TQFP44(new) [CX3003]  
ST72F324LJ4TC@TQFP44 [CX3003]  
ST72F324LJ4TC@TQFP44(new) [CX3003]  
ST72F324LJ6B3@SDIP42 [CX0042]  
ST72F324LJ6B3@SDIP42(new) [CX0042]  
ST72F324LJ6B5@SDIP42 [CX0042]  
ST72F324LJ6B5@SDIP42(new) [CX0042]  
ST72F324LJ6B6@SDIP42 [CX0042]  
ST72F324LJ6B6@SDIP42(new) [CX0042]  
ST72F324LJ6BA@SDIP42 [CX0042]  
ST72F324LJ6BA@SDIP42(new) [CX0042]  
ST72F324LJ6BC@SDIP42 [CX0042]  
ST72F324LJ6BC@SDIP42(new) [CX0042]  
ST72F324LJ6T3@TQFP44 [CX3003]  
ST72F324LJ6T3@TQFP44(new) [CX3003]  
ST72F324LJ6T5@TQFP44 [CX3003]  
ST72F324LJ6T5@TQFP44(new) [CX3003]  
ST72F324LJ6T6@TQFP44 [CX3003]  
ST72F324LJ6T6@TQFP44(new) [CX3003]  
ST72F324LJ6TA@TQFP44 [CX3003]  
ST72F324LJ6TA@TQFP44(new) [CX3003]  
ST72F324LJ6TC@TQFP44 [CX3003]  
ST72F324LJ6TC@TQFP44(new) [CX3003]  
ST72F324LK2B3@SDIP32 [CX0032]  
ST72F324LK2B3@SDIP32(new) [CX0032]  
ST72F324LK2B5@SDIP32 [CX0032]  
ST72F324LK2B5@SDIP32(new) [CX0032]  
ST72F324LK2B6@SDIP32 [CX0032]  
ST72F324LK2B6@SDIP32(new) [CX0032]  
ST72F324LK2BA@SDIP32 [CX0032]  
ST72F324LK2BA@SDIP32(new) [CX0032]  
ST72F324LK2BC@SDIP32 [CX0032]  
ST72F324LK2BC@SDIP32(new) [CX0032]  
ST72F324LK2T3@TQFP32 [CX3001]  
ST72F324LK2T3@TQFP32(new) [CX3001]  
ST72F324LK2T5@TQFP32 [CX3001]  
ST72F324LK2T5@TQFP32(new) [CX3001]  
ST72F324LK2T6@TQFP32 [CX3001]  
ST72F324LK2T6@TQFP32(new) [CX3001]  
ST72F324LK2TA@TQFP32 [CX3001]  
ST72F324LK2TA@TQFP32(new) [CX3001]  
ST72F324LK2TC@TQFP32 [CX3001]  
ST72F324LK2TC@TQFP32(new) [CX3001]  
ST72F324LK4B3@SDIP32 [CX0032]  
ST72F324LK4B3@SDIP32(new) [CX0032]  
ST72F324LK4B5@SDIP32 [CX0032]  
ST72F324LK4B5@SDIP32(new) [CX0032]  
ST72F324LK4B6@SDIP32 [CX0032]  
ST72F324LK4B6@SDIP32(new) [CX0032]  
ST72F324LK4BA@SDIP32 [CX0032]  
ST72F324LK4BA@SDIP32(new) [CX0032]  
ST72F324LK4BC@SDIP32 [CX0032]  
ST72F324LK4BC@SDIP32(new) [CX0032]  
ST72F324LK4T3@TQFP32 [CX3001]  
ST72F324LK4T3@TQFP32(new) [CX3001]



ST72F324LK4T5@TQFP32 [CX3001]  
ST72F324LK4T5@TQFP32(new) [CX3001]  
ST72F324LK4T6@TQFP32 [CX3001]  
ST72F324LK4T6@TQFP32(new) [CX3001]  
ST72F324LK4TA@TQFP32 [CX3001]  
ST72F324LK4TA@TQFP32(new) [CX3001]  
ST72F324LK4TC@TQFP32 [CX3001]  
ST72F324LK4TC@TQFP32(new) [CX3001]  
ST72F324LK6B3@SDIP32 [CX0032]  
ST72F324LK6B3@SDIP32(new) [CX0032]  
ST72F324LK6B5@SDIP32 [CX0032]  
ST72F324LK6B5@SDIP32(new) [CX0032]  
ST72F324LK6B6@SDIP32 [CX0032]  
ST72F324LK6B6@SDIP32(new) [CX0032]  
ST72F324LK6BA@SDIP32 [CX0032]  
ST72F324LK6BA@SDIP32(new) [CX0032]  
ST72F324LK6BC@SDIP32 [CX0032]  
ST72F324LK6BC@SDIP32(new) [CX0032]  
ST72F324LK6T3@TQFP32 [CX3001]  
ST72F324LK6T3@TQFP32(new) [CX3001]  
ST72F324LK6T5@TQFP32 [CX3001]  
ST72F324LK6T5@TQFP32(new) [CX3001]  
ST72F324LK6T6@TQFP32 [CX3001]  
ST72F324LK6T6@TQFP32(new) [CX3001]  
ST72F324LK6TA@TQFP32 [CX3001]  
ST72F324LK6TA@TQFP32(new) [CX3001]  
ST72F324LK6TC@TQFP32 [CX3001]  
ST72F324LK6TC@TQFP32(new) [CX3001]  
ST72F325AR6T3@TQFP64 [CX3011]  
ST72F325AR6T6@TQFP64 [CX3011]  
ST72F325AR7T5@TQFP64 [CX3011]  
ST72F325AR9T3@TQFP64 [CX3011]  
ST72F325AR9T6@TQFP64 [CX3011]  
ST72F325C4T5@TQFP48 [CX3007]  
ST72F325C6T3@TQFP48 [CX3007]  
ST72F325C6T6@TQFP48 [CX3007]  
ST72F325C7T5@TQFP48 [CX3007]  
ST72F325C9T3@TQFP48 [CX3007]  
ST72F325C9T6@TQFP48 [CX3007]  
ST72F325J4B5@SDIP42 [CX0042]  
ST72F325J4T3@TQFP44 [CX3003]  
ST72F325J4T6@TQFP44 [CX3003]  
ST72F325J6B5@SDIP42 [CX0042]  
ST72F325J6T3@TQFP44 [CX3003]  
ST72F325J6T6@TQFP44 [CX3003]  
ST72F325J7T5@TQFP44 [CX3003]  
ST72F325J9T3@TQFP44 [CX3003]  
ST72F325J9T6@TQFP44 [CX3003]  
ST72F325K4B5@SDIP32 [CX0032]  
ST72F325K4T3@TQFP32 [CX3001]  
ST72F325K4T6@TQFP32 [CX3001]  
ST72F325K6B5@SDIP32 [CX0032]  
ST72F325K6T3@TQFP32 [CX3001]  
ST72F325K6T6@TQFP32 [CX3001]  
ST72F325R6T5@TQFP64 [CX3013]  
ST72F325R7T3@TQFP64 [CX3013]  
ST72F325R7T6@TQFP64 [CX3013]  
ST72F325R9T5@TQFP64 [CX3013]  
ST72F32AJ1B5@SDIP42 [CX0042]

ST72F325AR6T5@TQFP64 [CX3011]  
ST72F325AR7T3@TQFP64 [CX3011]  
ST72F325AR7T6@TQFP64 [CX3011]  
ST72F325AR9T5@TQFP64 [CX3011]  
ST72F325C4T3@TQFP48 [CX3007]  
ST72F325C4T6@TQFP48 [CX3007]  
ST72F325C6T5@TQFP48 [CX3007]  
ST72F325C7T3@TQFP48 [CX3007]  
ST72F325C7T6@TQFP48 [CX3007]  
ST72F325C9T5@TQFP48 [CX3007]  
ST72F325J4B3@SDIP42 [CX0042]  
ST72F325J4B6@SDIP42 [CX0042]  
ST72F325J4T5@TQFP44 [CX3003]  
ST72F325J6B3@SDIP42 [CX0042]  
ST72F325J6B6@SDIP42 [CX0042]  
ST72F325J6T5@TQFP44 [CX3003]  
ST72F325J7T3@TQFP44 [CX3003]  
ST72F325J7T6@TQFP44 [CX3003]  
ST72F325J9T5@TQFP44 [CX3003]  
ST72F325K4B3@SDIP32 [CX0032]  
ST72F325K4B6@SDIP32 [CX0032]  
ST72F325K4T5@TQFP32 [CX3001]  
ST72F325K6B3@SDIP32 [CX0032]  
ST72F325K6B6@SDIP32 [CX0032]  
ST72F325K6T5@TQFP32 [CX3001]  
ST72F325R6T3@TQFP64 [CX3013]  
ST72F325R6T6@TQFP64 [CX3013]  
ST72F325R7T5@TQFP64 [CX3013]  
ST72F325R9T3@TQFP64 [CX3013]  
ST72F325R9T6@TQFP64 [CX3013]  
ST72F32AJ1B6@SDIP42 [CX0042]

ST72F32AJ1T5@TQFP44 [CX3003]  
ST72F32AJ2B5@SDIP42 [CX0042]  
ST72F32AJ2T5@TQFP44 [CX3003]  
ST72F32AJ2TA@TQFP44 [CX3003]  
ST72F32AJ2TC@TQFP44 [CX3003]  
ST72F32AK1B6@SDIP32 [CX0032]  
ST72F32AK1T6@TQFP32 [CX3001]  
ST72F32AK2B6@SDIP32 [CX0032]  
ST72F32AK2T6@TQFP32 [CX3001]  
ST72F32AK2TB@TQFP32 [CX3001]  
ST72F340K2T6@TQFP32 [CX3001]  
ST72F340S2T6@TQFP44 [CX3003]  
ST72F344K2T6@TQFP32 [CX3001]  
ST72F344S2T6@TQFP44 [CX3003]  
ST72F345C2T6@TQFP48 [CX3007]  
ST72F361AR4T3@TQFP64 [CX3011]  
ST72F361AR4TA@TQFP64 [CX3011]  
ST72F361AR6T3@TQFP64 [CX3011]  
ST72F361AR6TA@TQFP64 [CX3011]  
ST72F361AR7T3@TQFP64 [CX3011]  
ST72F361AR7TA@TQFP64 [CX3011]  
ST72F361AR9T3@TQFP64 [CX3011]  
ST72F361AR9TA@TQFP64 [CX3011]  
ST72F361J4T3@TQFP44 [CX3003]  
ST72F361J4TA@TQFP44 [CX3003]  
ST72F361J6T3@TQFP44 [CX3003]  
ST72F361J6TA@TQFP44 [CX3003]  
ST72F361J7T3@TQFP44 [CX3003]  
ST72F361J7TA@TQFP44 [CX3003]  
ST72F361J9T3@TQFP44 [CX3003]  
ST72F361J9TA@TQFP44 [CX3003]  
ST72F361K4T3@TQFP32 [CX3001]  
ST72F361K4TA@TQFP32 [CX3001]  
ST72F361K6T3@TQFP32 [CX3001]  
ST72F361K6TA@TQFP32 [CX3001]  
ST72F361K7T3@TQFP32 [CX3001]  
ST72F361K7TA@TQFP32 [CX3001]  
ST72F361K9T3@TQFP32 [CX3001]  
ST72F361K9TA@TQFP32 [CX3001]  
ST72F361R4T3@TQFP64 [CX3012]  
ST72F361R4TA@TQFP64 [CX3012]  
ST72F361R6T3@TQFP64 [CX3012]  
ST72F361R6TA@TQFP64 [CX3012]  
ST72F361R7T3@TQFP64 [CX3012]  
ST72F361R7TA@TQFP64 [CX3012]  
ST72F361R9T3@TQFP64 [CX3012]  
ST72F361R9TA@TQFP64 [CX3012]  
ST72F521AR6T3@TQFP64 [CX3011]  
ST72F521AR6TC@TQFP64 [CX3011]  
ST72F521AR9T6@TQFP64 [CX3011]  
ST72F521BAR6T3@TQFP64 [CX3011]  
ST72F521BAR6TC@TQFP64 [CX3011]  
ST72F521BAR9T6@TQFP64 [CX3011]  
ST72F521BM9T3@TQFP80 [CX3054]  
ST72F521BM9TC@TQFP80 [CX3054]  
ST72F521BR6T6@TQFP64 [CX3013]  
ST72F521BR9T3@TQFP64 [CX3013]  
ST72F521BR9TC@TQFP64 [CX3013]  
ST72F521M9T6@TQFP80 [CX3054]

ST72F32AJ1T6@TQFP44 [CX3003]  
ST72F32AJ2B6@SDIP42 [CX0042]  
ST72F32AJ2T6@TQFP44 [CX3003]  
ST72F32AJ2TB@TQFP44 [CX3003]  
ST72F32AK1B5@SDIP32 [CX0032]  
ST72F32AK1T5@TQFP32 [CX3001]  
ST72F32AK2B5@SDIP32 [CX0032]  
ST72F32AK2T5@TQFP32 [CX3001]  
ST72F32AK2TA@TQFP32 [CX3001]  
ST72F32AK2TC@TQFP32 [CX3001]  
ST72F340K4T6@TQFP32 [CX3001]  
ST72F340S4T6@TQFP44 [CX3003]  
ST72F344K4T6@TQFP32 [CX3001]  
ST72F344S4T6@TQFP44 [CX3003]  
ST72F345C4T6@TQFP48 [CX3007]  
ST72F361AR4T6@TQFP64 [CX3011]  
ST72F361AR4TC@TQFP64 [CX3011]  
ST72F361AR6T6@TQFP64 [CX3011]  
ST72F361AR6TC@TQFP64 [CX3011]  
ST72F361AR7T6@TQFP64 [CX3011]  
ST72F361AR7TC@TQFP64 [CX3011]  
ST72F361AR9T6@TQFP64 [CX3011]  
ST72F361AR9TC@TQFP64 [CX3011]  
ST72F361J4T6@TQFP44 [CX3003]  
ST72F361J4TC@TQFP44 [CX3003]  
ST72F361J6T6@TQFP44 [CX3003]  
ST72F361J6TC@TQFP44 [CX3003]  
ST72F361J7T6@TQFP44 [CX3003]  
ST72F361J7TC@TQFP44 [CX3003]  
ST72F361J9T6@TQFP44 [CX3003]  
ST72F361J9TC@TQFP44 [CX3003]  
ST72F361K4T6@TQFP32 [CX3001]  
ST72F361K4TC@TQFP32 [CX3001]  
ST72F361K6T6@TQFP32 [CX3001]  
ST72F361K6TC@TQFP32 [CX3001]  
ST72F361K7T6@TQFP32 [CX3001]  
ST72F361K7TC@TQFP32 [CX3001]  
ST72F361K9T6@TQFP32 [CX3001]  
ST72F361K9TC@TQFP32 [CX3001]  
ST72F361R4T6@TQFP64 [CX3012]  
ST72F361R4TC@TQFP64 [CX3012]  
ST72F361R6T6@TQFP64 [CX3012]  
ST72F361R6TC@TQFP64 [CX3012]  
ST72F361R7T6@TQFP64 [CX3012]  
ST72F361R7TC@TQFP64 [CX3012]  
ST72F361R9T6@TQFP64 [CX3012]  
ST72F361R9TC@TQFP64 [CX3012]  
ST72F521AR6T6@TQFP64 [CX3011]  
ST72F521AR9T3@TQFP64 [CX3011]  
ST72F521AR9TC@TQFP64 [CX3011]  
ST72F521BAR6T6@TQFP64 [CX3011]  
ST72F521BAR9T3@TQFP64 [CX3011]  
ST72F521BAR9TC@TQFP64 [CX3011]  
ST72F521BM9T6@TQFP80 [CX3054]  
ST72F521BR6T3@TQFP64 [CX3013]  
ST72F521BR6TC@TQFP64 [CX3013]  
ST72F521BR9T6@TQFP64 [CX3013]  
ST72F521M9T3@TQFP80 [CX3054]  
ST72F521M9TC@TQFP80 [CX3054]

ST72F521R6T3@TQFP64 [CX3013]  
ST72F521R6TC@TQFP64 [CX3013]  
ST72F521R9T6@TQFP64 [CX3013]  
ST72F561AR4T3@TQFP64 [CX3011]  
ST72F561AR4TA@TQFP64 [CX3011]  
ST72F561AR6T3@TQFP64 [CX3011]  
ST72F561AR6TA@TQFP64 [CX3011]  
ST72F561AR7T3@TQFP64 [CX3011]  
ST72F561AR7TA@TQFP64 [CX3011]  
ST72F561AR9T3@TQFP64 [CX3011]  
ST72F561AR9TA@TQFP64 [CX3011]  
ST72F561J4T3@TQFP44 [CX3003]  
ST72F561J4TA@TQFP44 [CX3003]  
ST72F561J6T3@TQFP44 [CX3003]  
ST72F561J6TA@TQFP44 [CX3003]  
ST72F561J7T3@TQFP44 [CX3003]  
ST72F561J7TA@TQFP44 [CX3003]  
ST72F561J9T3@TQFP44 [CX3003]  
ST72F561J9TA@TQFP44 [CX3003]  
ST72F561K4T3@TQFP32 [CX3001]  
ST72F561K4TA@TQFP32 [CX3001]  
ST72F561K6T3@TQFP32 [CX3001]  
ST72F561K6TA@TQFP32 [CX3001]  
ST72F561K7T3@TQFP32 [CX3001]  
ST72F561K7TA@TQFP32 [CX3001]  
ST72F561K9T3@TQFP32 [CX3001]  
ST72F561K9TA@TQFP32 [CX3001]  
ST72F561R4T3@TQFP64 [CX3013]  
ST72F561R4TA@TQFP64 [CX3013]  
ST72F561R6T3@TQFP64 [CX3013]  
ST72F561R6TA@TQFP64 [CX3013]  
ST72F561R7T3@TQFP64 [CX3013]  
ST72F561R7TA@TQFP64 [CX3013]  
ST72F561R9T3@TQFP64 [CX3013]  
ST72F561R9TA@TQFP64 [CX3013]  
ST72F60BD4U1@QFN40 [CX4017]  
ST72F60BE1M1@SOIC24 [CX1033]  
ST72F60BE4M1@SOIC24 [CX1033]  
ST72F60BK1U1@QFN40 [CX4017]  
ST72F60D4U1@QFN40 [CX4017]  
ST72F60E1M1@SOIC24 [CX1033]  
ST72F60E4M1@SOIC24 [CX1033]  
ST72F60K1U1@QFN40 [CX4017]  
ST72F621J4B1@SDIP42 [CX0042]  
ST72F621K4B1@SDIP32 [CX0032]  
ST72F622L2M1@SOIC34 [CX1037]  
ST72F623F2M1@SOIC20 [CX1033]  
ST72F63BD6U1@QFN40 [CX4017]  
ST72F63BE2M1@SOIC24 [CX1033]  
ST72F63BE6M1@SOIC24 [CX1033]  
ST72F63BH2T1@TQFP48 [CX3007]  
ST72F63BH6T1@TQFP48 [CX3007]  
ST72F63BK1M1@SOIC34 [CX1037]  
ST72F63BK2B1@SDIP32 [CX0032]  
ST72F63BK2U1@QFN40 [CX4017]  
ST72F63BK4M1@SOIC34 [CX1037]  
ST72F63BK6M1@SOIC34 [CX1037]  
ST72F63D6U1@QFN40 [CX4017]  
ST72F63E2M1@SOIC24 [CX1033]

ST72F521R6T6@TQFP64 [CX3013]  
ST72F521R9T3@TQFP64 [CX3013]  
ST72F521R9TC@TQFP64 [CX3013]  
ST72F561AR4T6@TQFP64 [CX3011]  
ST72F561AR4TC@TQFP64 [CX3011]  
ST72F561AR6T6@TQFP64 [CX3011]  
ST72F561AR6TC@TQFP64 [CX3011]  
ST72F561AR7T6@TQFP64 [CX3011]  
ST72F561AR7TC@TQFP64 [CX3011]  
ST72F561AR9T6@TQFP64 [CX3011]  
ST72F561AR9TC@TQFP64 [CX3011]  
ST72F561J4T6@TQFP44 [CX3003]  
ST72F561J4TC@TQFP44 [CX3003]  
ST72F561J6T6@TQFP44 [CX3003]  
ST72F561J6TC@TQFP44 [CX3003]  
ST72F561J7T6@TQFP44 [CX3003]  
ST72F561J7TC@TQFP44 [CX3003]  
ST72F561J9T6@TQFP44 [CX3003]  
ST72F561J9TC@TQFP44 [CX3003]  
ST72F561K4T6@TQFP32 [CX3001]  
ST72F561K4TC@TQFP32 [CX3001]  
ST72F561K6T6@TQFP32 [CX3001]  
ST72F561K6TC@TQFP32 [CX3001]  
ST72F561K7T6@TQFP32 [CX3001]  
ST72F561K7TC@TQFP32 [CX3001]  
ST72F561K9T6@TQFP32 [CX3001]  
ST72F561K9TC@TQFP32 [CX3001]  
ST72F561R4T6@TQFP64 [CX3013]  
ST72F561R4TC@TQFP64 [CX3013]  
ST72F561R6T6@TQFP64 [CX3013]  
ST72F561R6TC@TQFP64 [CX3013]  
ST72F561R7T6@TQFP64 [CX3013]  
ST72F561R7TC@TQFP64 [CX3013]  
ST72F561R9T6@TQFP64 [CX3013]  
ST72F561R9TC@TQFP64 [CX3013]  
ST72F60BD6U1@QFN40 [CX4017]  
ST72F60BE2M1@SOIC24 [CX1033]  
ST72F60BE6M1@SOIC24 [CX1033]  
ST72F60BK2U1@QFN40 [CX4017]  
ST72F60D6U1@QFN40 [CX4017]  
ST72F60E2M1@SOIC24 [CX1033]  
ST72F60E6M1@SOIC24 [CX1033]  
ST72F60K2U1@QFN40 [CX4017]  
ST72F621J4T1@TQFP44 [CX3003]  
ST72F621L4M1@SOIC34 [CX1037]  
ST72F623F2B1 [CX0001]  
ST72F63BD4U1@QFN40 [CX4017]  
ST72F63BE1M1@SOIC24 [CX1033]  
ST72F63BE4M1@SOIC24 [CX1033]  
ST72F63BH1T1@TQFP48 [CX3007]  
ST72F63BH4T1@TQFP48 [CX3007]  
ST72F63BK1B1@SDIP32 [CX0032]  
ST72F63BK1U1@QFN40 [CX4017]  
ST72F63BK2M1@SOIC34 [CX1037]  
ST72F63BK4B1@SDIP32 [CX0032]  
ST72F63BK6B1@SDIP32 [CX0032]  
ST72F63D4U1@QFN40 [CX4017]  
ST72F63E1M1@SOIC24 [CX1033]  
ST72F63E4M1@SOIC24 [CX1033]

ST72F63E6M1@SOIC24 [CX1033]  
ST72F63H2T1@TQFP48 [CX3007]  
ST72F63H6T1@TQFP48 [CX3007]  
ST72F63K1M1@SOIC34 [CX1037]  
ST72F63K2B1@SDIP32 [CX0032]  
ST72F63K2U1@QFN40 [CX4017]  
ST72F63K4M1@SOIC34 [CX1037]  
ST72F63K6M1@SOIC34 [CX1037]  
ST72F651AR6T1E@TQFP64 [CX3011]  
ST72F651R6T1E@TQFP64 [CX3012]  
ST7FAUDIOAR6@TQFP64 [CX3011]  
ST7FDALIF2M6@SOIC20 [CX1033]  
ST7FDALIF2M6@SOIC20(ISP) [CX0001]  
ST7FLI49MK1B6 [CX0032]  
ST7FLIT10BF0B3 [CX0001]  
ST7FLIT10BF0M3@SOIC20 [CX1033]  
ST7FLIT10BF1B3 [CX0001]  
ST7FLIT10BF1M3@SOIC20 [CX1033]  
ST7FLIT10BY0B3 [CX0001]  
ST7FLIT10BY0M3@SOIC16 [CX1016]  
ST7FLIT10BY1B3 [CX0001]  
ST7FLIT10BY1M3@SOIC16 [CX1016]  
ST7FLIT15BF0B3 [CX0001]  
ST7FLIT15BF0M3@SOIC20 [CX1033]  
ST7FLIT15BF1B3 [CX0001]  
ST7FLIT15BF1M3@SOIC20 [CX1033]  
ST7FLIT15BF1U6TR@QFN20 [CX4011]  
ST7FLIT15BY0B6 [CX0001]  
ST7FLIT15BY0M6@SOIC16 [CX1016]  
ST7FLIT15BY1B6 [CX0001]  
ST7FLIT15BY1M6@SOIC16 [CX1016]  
ST7FLIT19BF0B6 [CX0001]  
ST7FLIT19BF0M6@SOIC20 [CX1033]  
ST7FLIT19BF1B6 [CX0001]  
ST7FLIT19BF1M6@SOIC20 [CX1033]  
ST7FLIT19BY0B3 [CX0001]  
ST7FLIT19BY0M3@SOIC16 [CX1016]  
ST7FLIT19BY1B3 [CX0001]  
ST7FLIT19BY1M3@SOIC16 [CX1016]  
ST7FLITE02B6 [CX0001]  
ST7FLITE02M6@SOIC16(ISP) [CX0001]  
ST7FLITE02Y0B6 [CX0001]  
ST7FLITE02Y0M6@SOIC16 [CX1016]  
ST7FLITE02Y0M6@SOIC16(ISP) [CX0001]  
ST7FLITE05B6 [CX0001]  
ST7FLITE05M6@SOIC16(ISP) [CX0001]  
ST7FLITE05Y0B6 [CX0001]  
ST7FLITE05Y0M6@SOIC16 [CX1016]  
ST7FLITE05Y0M6@SOIC16(ISP) [CX0001]  
ST7FLITE09B6 [CX0001]  
ST7FLITE09M6@SOIC16(ISP) [CX0001]  
ST7FLITE09Y0B6 [CX0001]  
ST7FLITE09Y0M6@SOIC16 [CX1016]  
ST7FLITE09Y0M6@SOIC16(ISP) [CX0001]  
ST7FLITE10F1B6 [CX0001]  
ST7FLITE10F1M6@SOIC20 [CX1033]  
ST7FLITE10F1M6@SOIC20(ISP) [CX0001]  
ST7FLITE15F1B6 [CX0001]  
ST7FLITE15F1M6@SOIC20 [CX1033]

ST72F63H1T1@TQFP48 [CX3007]  
ST72F63H4T1@TQFP48 [CX3007]  
ST72F63K1B1@SDIP32 [CX0032]  
ST72F63K1U1@QFN40 [CX4017]  
ST72F63K2M1@SOIC34 [CX1037]  
ST72F63K4B1@SDIP32 [CX0032]  
ST72F63K6B1@SDIP32 [CX0032]  
ST72F651AR6T1@TQFP64 [CX3011]  
ST72F651R6T1@TQFP64 [CX3012]  
ST7FAUDIO@TQFP64 [CX3011]  
ST7FAUDIOAR9@TQFP64 [CX3011]  
ST7FLI49MK1T6@QFP32 [CX3001]  
ST7FLIT10BF0B6 [CX0001]  
ST7FLIT10BF0M6@SOIC20 [CX1033]  
ST7FLIT10BF1B6 [CX0001]  
ST7FLIT10BF1M6@SOIC20 [CX1033]  
ST7FLIT10BY0B6 [CX0001]  
ST7FLIT10BY0M6@SOIC16 [CX1016]  
ST7FLIT10BY1B6 [CX0001]  
ST7FLIT10BY1M6@SOIC16 [CX1016]  
ST7FLIT15BF0B6 [CX0001]  
ST7FLIT15BF0M6@SOIC20 [CX1033]  
ST7FLIT15BF1B6 [CX0001]  
ST7FLIT15BF1M6@SOIC20 [CX1033]  
ST7FLIT15BY0B3 [CX0001]  
ST7FLIT15BY0M3@SOIC16 [CX1016]  
ST7FLIT15BY1B3 [CX0001]  
ST7FLIT15BY1M3@SOIC16 [CX1016]  
ST7FLIT19BF0B3 [CX0001]  
ST7FLIT19BF0M3@SOIC20 [CX1033]  
ST7FLIT19BF1B3 [CX0001]  
ST7FLIT19BF1M3@SOIC20 [CX1033]  
ST7FLIT19BF1U6TR@QFN20 [CX4011]  
ST7FLIT19BY0B6 [CX0001]  
ST7FLIT19BY0M6@SOIC16 [CX1016]  
ST7FLIT19BY1B6 [CX0001]  
ST7FLIT19BY1M6@SOIC16 [CX1016]  
ST7FLITE02M6@SOIC16 [CX1016]  
ST7FLITE02Y0B6(ISP) [CX0001]  
ST7FLITE05M6@SOIC16 [CX1016]  
ST7FLITE05Y0B6(ISP) [CX0001]  
ST7FLITE09M6@SOIC16 [CX1016]  
ST7FLITE09Y0B6(ISP) [CX0001]  
ST7FLITE10F1B6(ISP) [CX0001]  
ST7FLITE15F1B6(ISP) [CX0001]

ST7FLITE15F1M6@SOIC20(ISP) [CX0001]  
ST7FLITE19F1B6 [CX0001] ST7FLITE19F1B6(ISP) [CX0001]  
ST7FLITE19F1M6@SOIC20 [CX1033]  
ST7FLITE19F1M6@SOIC20(ISP) [CX0001]  
ST7FLITE20F2B6 [CX0001] ST7FLITE20F2B6(ISP) [CX0001]  
ST7FLITE20F2M6@SOIC20 [CX1033]  
ST7FLITE20F2M6@SOIC20(ISP) [CX0001]  
ST7FLITE25F2B6 [CX0001] ST7FLITE25F2B6(ISP) [CX0001]  
ST7FLITE25F2M6@SOIC20 [CX1033]  
ST7FLITE25F2M6@SOIC20(ISP) [CX0001]  
ST7FLITE29F2B6 [CX0001] ST7FLITE29F2B6(ISP) [CX0001]  
ST7FLITE29F2M6@SOIC20 [CX1033]  
ST7FLITE29F2M6@SOIC20(ISP) [CX0001]  
ST7FLITE30F2B6 [CX0001] ST7FLITE30F2B6(ISP) [CX0001]  
ST7FLITE30F2M6@SOIC20 [CX1033]  
ST7FLITE30F2M6@SOIC20(ISP) [CX0001]  
ST7FLITE33F2B6 [CX0001] ST7FLITE33F2B6(ISP) [CX0001]  
ST7FLITE33F2M6@SOIC20 [CX1033]  
ST7FLITE33F2M6@SOIC20(ISP) [CX0001]  
ST7FLITE35F2B6 [CX0001] ST7FLITE35F2B6(ISP) [CX0001]  
ST7FLITE35F2M6@SOIC20 [CX1033]  
ST7FLITE35F2M6@SOIC20(ISP) [CX0001]  
ST7FLITE39F2B6 [CX0001] ST7FLITE39F2B6(ISP) [CX0001]  
ST7FLITE39F2M6@SOIC20 [CX1033]  
ST7FLITE39F2M6@SOIC20(ISP) [CX0001]  
ST7FLITE49 [CX0032] ST7FLITE49@QFN40 [CX4017]  
ST7FLITE49@TQFP32 [CX3001] ST7FLITEBC [CX0001]  
ST7FLITEBCM6@SOIC16 [CX1016] ST7FLITES0  
ST7FLITES0@SOIC16 [CX1016] ST7FLITES2B6 [CX0001]  
ST7FLITES2M6@SOIC16 [CX1016]  
ST7FLITES2M6@SOIC16(ISP) [CX0001]  
ST7FLITES2Y0B6 [CX0001] ST7FLITES2Y0B6(ISP) [CX0001]  
ST7FLITES2Y0M6@SOIC16 [CX1016]  
ST7FLITES2Y0M6@SOIC16(ISP) [CX0001]  
ST7FLITES5B6 [CX0001] ST7FLITES5M6@SOIC16 [CX1016]  
ST7FLITES5M6@SOIC16(ISP) [CX0001]  
ST7FLITES5Y0B6 [CX0001] ST7FLITES5Y0B6(ISP) [CX0001]  
ST7FLITES5Y0M6@SOIC16 [CX1016]  
ST7FLITES5Y0M6@SOIC16(ISP) [CX0001]  
ST7FMC1K2B3@SDIP32 [CX0032] ST7FMC1K2B6@SDIP32 [CX0032]  
ST7FMC1K2BC@SDIP32 [CX0032] ST7FMC1K2T3@TQFP32 [CX3001]  
ST7FMC1K2T6@TQFP32 [CX3001] ST7FMC1K2TC@TQFP32 [CX3001]  
ST7FMC1K4B3@SDIP32 [CX0032] ST7FMC1K4B6@SDIP32 [CX0032]  
ST7FMC1K4BC@SDIP32 [CX0032] ST7FMC1K4T3@TQFP32 [CX3001]  
ST7FMC1K4T6@TQFP32 [CX3001] ST7FMC1K4TC@TQFP32 [CX3001]  
ST7FMC1K6B3@SDIP32 [CX0032] ST7FMC1K6B6@SDIP32 [CX0032]  
ST7FMC1K6BC@SDIP32 [CX0032] ST7FMC1K6T3@TQFP32 [CX3001]  
ST7FMC1K6T6@TQFP32 [CX3001] ST7FMC1K6TC@TQFP32 [CX3001]  
ST7FMC2M9T3@TQFP80 [CX3054] ST7FMC2M9T6@TQFP80 [CX3054]  
ST7FMC2M9TC@TQFP80 [CX3054] ST7FMC2N6B3@SDIP56 [CX0056]  
ST7FMC2N6B6@SDIP56 [CX0056] ST7FMC2N6BC@SDIP56 [CX0056]  
ST7FMC2N7B3@SDIP56 [CX0056] ST7FMC2N7B6@SDIP56 [CX0056]  
ST7FMC2N7BC@SDIP56 [CX0056] ST7FMC2R6T3@TQFP64 [CX3012]  
ST7FMC2R6T6@TQFP64 [CX3012] ST7FMC2R6TC@TQFP64 [CX3012]  
ST7FMC2R7T3@TQFP64 [CX3012] ST7FMC2R7T6@TQFP64 [CX3012]  
ST7FMC2R7TC@TQFP64 [CX3012] ST7FMC2S4T3@TQFP44 [CX3003]  
ST7FMC2S4T6@TQFP44 [CX3003] ST7FMC2S4TC@TQFP44 [CX3003]  
ST7FMC2S5T3@TQFP44 [CX3003] ST7FMC2S5T6@TQFP44 [CX3003]  
ST7FMC2S5TC@TQFP44 [CX3003] ST7FMC2S6T3@TQFP44 [CX3003]

ST7FMC2S6T6@TQFP44 [CX3003]  
ST7FMC2S7T3@TQFP44 [CX3003]  
ST7FMC2S7TC@TQFP44 [CX3003]  
ST7FOXF1M6 [CX1033]  
ST7FOXF2M6 [CX1033]  
ST7FOXK1T6 [CX3001]  
ST7FOXK2T6 [CX3001]  
ST7FSCR1R4T1@TQFP64 [CX3016]  
STM32F051C6@LQFP48 [CX3007]  
STM32F051K4@QFN32 [CX4015]  
STM32F051K8@QFN32 [CX4015]  
STM32F051R6@LQFP64 [CX3011]  
STM32F100C4@LQFP48 [CX3007]  
STM32F100C6@LQFP48 [CX3007]  
STM32F100C8@LQFP48 [CX3007]  
STM32F100CB@LQFP48 [CX3007]  
STM32F100R4@BGA64 [CX5141]  
STM32F100R4@LQFP64 [CX3011]  
STM32F100R6@BGA64 [CX5141]  
STM32F100R6@LQFP64 [CX3011]  
STM32F100R8@BGA64 [CX5141]  
STM32F100R8@LQFP64 [CX3011]  
STM32F100RB@BGA64 [CX5141]  
STM32F100RB@LQFP64 [CX3011]  
STM32F100RC@LQFP64 [CX3011]  
STM32F100RD@LQFP64 [CX3011]  
STM32F100RE@LQFP64 [CX3011]  
STM32F100V8@LQFP100 [CX3043]  
STM32F100V8@LQFP100(ISP) [CX0001]  
STM32F100VB@LQFP100 [CX3043]  
STM32F100VB@LQFP100(ISP) [CX0001]  
STM32F100VC@LQFP100 [CX3043]  
STM32F100VC@LQFP100(ISP) [CX0001]  
STM32F100VD@LQFP100 [CX3043]  
STM32F100VD@LQFP100(ISP) [CX0001]  
STM32F100VE@LQFP100 [CX3043]  
STM32F100VE@LQFP100(ISP) [CX0001]  
STM32F100ZC@LQFP144(ISP) [CX0001]  
STM32F100ZD@LQFP144(ISP) [CX0001]  
STM32F100ZE@LQFP144(ISP) [CX0001]  
STM32F101C4@LQFP48 [CX3007]  
STM32F101C4@LQFP48(UART) [CX3007]  
STM32F101C4@QFN48 [CX4021]  
STM32F101C6@LQFP48(UART) [CX3007]  
STM32F101C6@QFN48 [CX4021]  
STM32F101C8@LQFP48(UART) [CX3007]  
STM32F101C8@QFN48 [CX4021]  
STM32F101CB@LQFP48(UART) [CX3007]  
STM32F101CB@QFN48 [CX4021]  
STM32F101R4@LQFP64(UART) [CX3011]  
STM32F101R6@LQFP64 [CX3011]  
STM32F101R6@LQFP64(UART) [CX3011]  
STM32F101R8@LQFP64 [CX3011]  
STM32F101R8@LQFP64(UART) [CX3011]  
STM32F101RB@LQFP64 [CX3011]  
STM32F101RB@LQFP64(UART) [CX3011]  
STM32F101RC@LQFP64 [CX3011]  
STM32F101RC@LQFP64(UART) [CX3011]  
STM32F101RD@LQFP64 [CX3011]

ST7FMC2S6TC@TQFP44 [CX3003]  
ST7FMC2S7T6@TQFP44 [CX3003]  
ST7FOXF1B6 [CX0001]  
ST7FOXF2B6 [CX0001]  
ST7FOXK1B6 [CX0032]  
ST7FOXK2B6 [CX0032]  
ST7FSCR1E4M1@SOIC24 [CX1033]  
STM32F051C4@LQFP48 [CX3007]  
STM32F051C8@LQFP48 [CX3007]  
STM32F051K6@QFN32 [CX4015]  
STM32F051R4@LQFP64 [CX3011]  
STM32F051R8@LQFP64 [CX3011]  
STM32F100C4@LQFP48(ISP) [CX0001]  
STM32F100C6@LQFP48(ISP) [CX0001]  
STM32F100C8@LQFP48(ISP) [CX0001]  
STM32F100CB@LQFP48(ISP) [CX0001]  
STM32F100R4@BGA64(ISP) [CX0001]  
STM32F100R4@LQFP64(ISP) [CX0001]  
STM32F100R6@BGA64(ISP) [CX0001]  
STM32F100R6@LQFP64(ISP) [CX0001]  
STM32F100R8@BGA64(ISP) [CX0001]  
STM32F100R8@LQFP64(ISP) [CX0001]  
STM32F100RB@BGA64(ISP) [CX0001]  
STM32F100RB@LQFP64(ISP) [CX0001]  
STM32F100RC@LQFP64(ISP) [CX0001]  
STM32F100RD@LQFP64(ISP) [CX0001]  
STM32F100RE@LQFP64(ISP) [CX0001]

STM32F101C6@LQFP48 [CX3007]  
STM32F101C8@LQFP48 [CX3007]  
STM32F101CB@LQFP48 [CX3007]  
STM32F101R4@LQFP64 [CX3011]

STM32F101RD@LQFP64(UART) [CX3011]  
STM32F101RE@LQFP64 [CX3011]  
STM32F101RE@LQFP64(UART) [CX3011]  
STM32F101RF@LQFP64 [CX3011]  
STM32F101T4@QFN36 [CX4029]  
STM32F101T6@QFN36 [CX4029]  
STM32F101T8@QFN36 [CX4029]  
STM32F101TB@QFN36 [CX4029]  
STM32F101V8@LQFP100(UART) [CX3043]  
STM32F101VB@LQFP100 [CX3043]  
STM32F101VB@LQFP100(UART) [CX3043]  
STM32F101VC@LQFP100 [CX3043]  
STM32F101VC@LQFP100(UART) [CX3043]  
STM32F101VD@LQFP100 [CX3043]  
STM32F101VD@LQFP100(UART) [CX3043]  
STM32F101VE@LQFP100 [CX3043]  
STM32F101VE@LQFP100(UART) [CX3043]  
STM32F101VF@LQFP100 [CX3043]  
STM32F102C4@LQFP48 [CX3007]  
STM32F102C4@LQFP48(UART) [CX3007]  
STM32F102C6@LQFP48 [CX3007]  
STM32F102C6@LQFP48(UART) [CX3007]  
STM32F102C8@LQFP48 [CX3007]  
STM32F102C8@LQFP48(UART) [CX3007]  
STM32F102CB@LQFP48 [CX3007]  
STM32F102CB@LQFP48(UART) [CX3007]  
STM32F102R4@LQFP64 [CX3011]  
STM32F102R4@LQFP64(UART) [CX3011]  
STM32F102R6@LQFP64 [CX3011]  
STM32F102R6@LQFP64(UART) [CX3011]  
STM32F102R8@LQFP64 [CX3011]  
STM32F102R8@LQFP64(UART) [CX3011]  
STM32F102RB@LQFP64 [CX3011]  
STM32F102RB@LQFP64(UART) [CX3011]  
STM32F103C4@LQFP48 [CX3007]  
STM32F103C4@LQFP48(UART) [CX3007]  
STM32F103C4@QFN48 [CX4021]  
STM32F103C6@LQFP48(UART) [CX3007]  
STM32F103C6@QFN48 [CX4021]  
STM32F103C8@LQFP48(UART) [CX3007]  
STM32F103C8@QFN48 [CX4021]  
STM32F103CB@LQFP48(UART) [CX3007]  
STM32F103CB@QFN48 [CX4021]  
STM32F103R4@LQFP64 [CX3011]  
STM32F103R4@LQFP64(UART) [CX3011]  
STM32F103R6@FBGA64 [CX5141]  
STM32F103R6@LQFP64(UART) [CX3011]  
STM32F103R8@FBGA64 [CX5141]  
STM32F103R8@LQFP64(UART) [CX3011]  
STM32F103RB@FBGA64 [CX5141]  
STM32F103RB@LQFP64(UART) [CX3011]  
STM32F103RC@LQFP64 [CX3011]  
STM32F103RC@LQFP64(UART) [CX3011]  
STM32F103RC@WLCSP64 [CX5193]  
STM32F103RD@LQFP64(UART) [CX3011]  
STM32F103RD@WLCSP64 [CX5193]  
STM32F103RE@LQFP64(UART) [CX3011]  
STM32F103RE@WLCSP64 [CX5193]  
STM32F103RG@LQFP64 [CX3011]  
STM32F101RG@LQFP64 [CX3011]  
STM32F101T4@QFN36(UART) [CX4029]  
STM32F101T6@QFN36(UART) [CX4029]  
STM32F101T8@QFN36(UART) [CX4029]  
STM32F101V8@LQFP100 [CX3043]  
STM32F101VG@LQFP100 [CX3043]  
STM32F103C6@LQFP48 [CX3007]  
STM32F103C8@LQFP48 [CX3007]  
STM32F103CB@LQFP48 [CX3007]  
STM32F103R4@FBGA64 [CX5141]  
STM32F103R6@LQFP64 [CX3011]  
STM32F103R8@LQFP64 [CX3011]  
STM32F103RB@LQFP64 [CX3011]  
STM32F103RD@LQFP64 [CX3011]  
STM32F103RE@LQFP64 [CX3011]  
STM32F103RF@LQFP64 [CX3011]  
STM32F103T4@QFN36 [CX4029]

STM32F103T4@QFN36(UART) [CX4029] STM32F103T6@QFN36 [CX4029]  
STM32F103T6@QFN36(UART) [CX4029] STM32F103T8@QFN36 [CX4029]  
STM32F103T8@QFN36(UART) [CX4029] STM32F103TB@QFN36 [CX4029]  
STM32F103V8@BGA100 [CX5106]  
STM32F103V8@BGA100(UART) [CX5106]  
STM32F103V8@LQFP100 [CX3043]  
STM32F103V8@LQFP100(UART) [CX3043]  
STM32F103VB@BGA100 [CX5106]  
STM32F103VB@BGA100(UART) [CX5106]  
STM32F103VB@LQFP100 [CX3043]  
STM32F103VB@LQFP100(UART) [CX3043]  
STM32F103VC@BGA100 [CX5106]  
STM32F103VC@BGA100(UART) [CX5106]  
STM32F103VC@LQFP100 [CX3043]  
STM32F103VC@LQFP100(UART) [CX3043]  
STM32F103VD@BGA100 [CX5106]  
STM32F103VD@BGA100(UART) [CX5106]  
STM32F103VD@LQFP100 [CX3043]  
STM32F103VD@LQFP100(UART) [CX3043]  
STM32F103VE@BGA100 [CX5106]  
STM32F103VE@BGA100(UART) [CX5106]  
STM32F103VE@LQFP100 [CX3043]  
STM32F103VE@LQFP100(UART) [CX3043]  
STM32F103VF@LQFP100 [CX3043] STM32F103VG@LQFP100 [CX3043]  
STM32F105R8@LQFP64 [CX3011] STM32F105RB@LQFP64 [CX3011]  
STM32F105RC@LQFP64 [CX3011] STM32F105V8@LQFP100 [CX3043]  
STM32F105VB@BGA100 [CX5106] STM32F105VB@LQFP100 [CX3043]  
STM32F105VC@BGA100 [CX5106] STM32F105VC@LQFP100 [CX3043]  
STM32F107RB@LQFP64 [CX3011] STM32F107RC@LQFP64 [CX3011]  
STM32F107VB@LQFP100 [CX3043] STM32F107VC@LQFP100 [CX3043]  
STM32F205RB@LQFP64 [CX3011] STM32F205RC@LQFP64 [CX3011]  
STM32F205RE@LQFP64 [CX3011] STM32F205RF@LQFP64 [CX3011]  
STM32F205RG@LQFP64 [CX3011] STM32F205VB@LQFP100 [CX3043]  
STM32F205VC@LQFP100 [CX3043] STM32F205VE@LQFP100 [CX3043]  
STM32F205VF@LQFP100 [CX3043] STM32F205VG@LQFP100 [CX3043]  
STM32F207VC@LQFP100 [CX3043] STM32F207VE@LQFP100 [CX3043]  
STM32F207VF@LQFP100 [CX3043] STM32F207VG@LQFP100 [CX3043]  
STM32L151C6@LQFP48 [CX3007] STM32L151C6@QFN48 [CX4021]  
STM32L151C8@LQFP48 [CX3007] STM32L151C8@QFN48 [CX4021]  
STM32L151CB@LQFP48 [CX3007] STM32L151CB@QFN48 [CX4021]  
STM32L151R6@BGA64 [CX5141] STM32L151R6@LQFP64 [CX3011]  
STM32L151R8@BGA64 [CX5141] STM32L151R8@LQFP64 [CX3011]  
STM32L151RB@BGA64 [CX5141] STM32L151RB@LQFP64 [CX3011]  
STM32L151RC@LQFP64 [CX3011] STM32L151RD@LQFP64 [CX3011]  
STM32L151V8@BGA100 [CX5150] STM32L151V8@LQFP100 [CX3043]  
STM32L151VB@BGA100 [CX5150] STM32L151VB@LQFP100 [CX3043]  
STM32L151VC@LQFP100 [CX3043] STM32L151VD@LQFP100 [CX3043]  
STM32L152C6@LQFP48 [CX3007] STM32L152C6@QFN48 [CX4021]  
STM32L152C8@LQFP48 [CX3007] STM32L152C8@QFN48 [CX4021]  
STM32L152CB@LQFP48 [CX3007] STM32L152CB@QFN48 [CX4021]  
STM32L152R6@BGA64 [CX5141] STM32L152R6@LQFP64 [CX3011]  
STM32L152R8@BGA64 [CX5141] STM32L152R8@LQFP64 [CX3011]  
STM32L152RB@BGA64 [CX5141] STM32L152RB@LQFP64 [CX3011]  
STM32L152RC@LQFP64 [CX3011] STM32L152RD@LQFP64 [CX3011]  
STM32L152V8@BGA100 [CX5150] STM32L152V8@LQFP100 [CX3043]  
STM32L152VB@BGA100 [CX5150] STM32L152VB@LQFP100 [CX3043]  
STM32L152VC@LQFP100 [CX3043] STM32L152VD@LQFP100 [CX3043]  
STM32L162RD@LQFP64 [CX3011] STM32L162VD@LQFP100 [CX3043]  
STM32W108C8@QFN48 [CX4021] STM32W108CB@QFN48 [CX4021]



STM32W108CC@QFN48 [CX4021]	STM32W108CZ@QFN48 [CX4021]
STM32W108HB@QFN40 [CX4017]	STM8L051F3@TSSOP20 [CX1067-2]
STM8L052C6@LQFP48 [CX3007-3]	STM8L052R8@LQFP64 [CX3011-4]
STM8L101F1@QFN20 [CX4041-2]	STM8L101F1@TSSOP20 [CX1067-2]
STM8L101F2@QFN20 [CX4041-2]	STM8L101F2@TSSOP20 [CX1067-2]
STM8L101F3@QFN20 [CX4041-2]	STM8L101F3@TSSOP20 [CX1067-2]
STM8L101G2@QFN28 [CX4083-2]	STM8L101G3@QFN28 [CX4083-2]
STM8L101K3@LQFP32 [CX3001-2]	STM8L101K3@QFN32 [CX4015-2]
STM8L151C2@LQFP48 [CX3007-3]	STM8L151C3@LQFP48 [CX3007-3]
STM8L151C4@LQFP48 [CX3007-3]	STM8L151C4@QFN48 [CX4021-1]
STM8L151C6@LQFP48 [CX3007-3]	STM8L151C6@QFN48 [CX4021-1]
STM8L151C8@LQFP48 [CX3007-3]	STM8L151C8@QFN48 [CX4021-1]
STM8L151F2@QFN20 [CX4041-2]	STM8L151F2@TSSOP20 [CX1067-2]
STM8L151F3@QFN20 [CX4041-2]	STM8L151F3@TSSOP20 [CX1067-2]
STM8L151G2@QFN28 [CX4083-2]	STM8L151G3@QFN28 [CX4083-2]
STM8L151G4@QFN28 [CX4083-2]	STM8L151G6@QFN28 [CX4083-2]
STM8L151K2@QFN32 [CX4015-2]	STM8L151K3@QFN32 [CX4015-2]
STM8L151K4@LQFP32 [CX3001-2]	STM8L151K4@QFN32 [CX4015-2]
STM8L151K6@LQFP32 [CX3001-2]	STM8L151K6@QFN32 [CX4015-2]
STM8L151M8@LQFP80 [CX3017-2]	STM8L151R6@LQFP64 [CX3011-4]
STM8L151R8@LQFP64 [CX3011-4]	STM8L152C4@LQFP48 [CX3007-3]
STM8L152C4@QFN48 [CX4021-1]	STM8L152C6@LQFP48 [CX3007-3]
STM8L152C6@QFN48 [CX4021-1]	STM8L152C8@LQFP48 [CX3007-3]
STM8L152C8@QFN48 [CX4021-1]	STM8L152K4@LQFP32 [CX3001-2]
STM8L152K4@QFN32 [CX4015-2]	STM8L152K6@LQFP32 [CX3001-2]
STM8L152K6@QFN32 [CX4015-2]	STM8L152M8@LQFP80 [CX3017-2]
STM8L152R6@LQFP64 [CX3011-4]	STM8L152R8@LQFP64 [CX3011-4]
STM8S003F3@QFN20 [CX4041-1]	STM8S003F3@TSSOP20 [CX1067-1]
STM8S003K3@LQFP32 [CX3001-1]	STM8S005C6@LQFP48 [CX3007-1]
STM8S005K6@LQFP32 [CX3001-1]	STM8S007C8@QFP48 [CX3007-1]
STM8S103F2@QFN20 [CX4041-1]	STM8S103F2@TSSOP20 [CX1067-1]
STM8S103F3@QFN20 [CX4041-1]	STM8S103F3@TSSOP20 [CX1067-1]
STM8S103K3@LQFP32 [CX3001-1]	STM8S103K3@QFN32 [CX4015-1]
STM8S105C4@LQFP48 [CX3007-1]	STM8S105C6@LQFP48 [CX3007-1]
STM8S105K4@LQFP32 [CX3001-1]	STM8S105K4@QFN32 [CX4015-1]
STM8S105K4@SDIP32 [CX0032-1]	STM8S105K6@LQFP32 [CX3001-1]
STM8S105K6@QFN32 [CX4015-1]	STM8S105K6@SDIP32 [CX0032-1]
STM8S105S4@LQFP44 [CX3005-1]	STM8S105S6@LQFP44 [CX3005-1]
STM8S207C6@LQFP48 [CX3007-1]	STM8S207C8@LQFP48 [CX3007-1]
STM8S207CB@LQFP48 [CX3007-1]	STM8S207K6@LQFP32 [CX3001-1]
STM8S207M8@LQFP80 [CX3017-1]	STM8S207MB@LQFP80 [CX3017-1]
STM8S207R6@LQFP64[10*10] [CX3011-1]	
STM8S207R6@LQFP64[14*14] [CX3044-1]	
STM8S207R8@LQFP64[10*10] [CX3011-1]	
STM8S207R8@LQFP64[14*14] [CX3044-1]	
STM8S207RB@LQFP64[10*10] [CX3011-1]	
STM8S207RB@LQFP64[14*14] [CX3044-1]	
STM8S207S6@LQFP44 [CX3005-1]	STM8S207S8@LQFP44 [CX3005-1]
STM8S207SB@LQFP44 [CX3005-1]	STM8S208C6@LQFP48 [CX3007-1]
STM8S208C8@LQFP48 [CX3007-1]	STM8S208CB@LQFP48 [CX3007-1]
STM8S208MB@LQFP80 [CX3017-1]	
STM8S208R6@LQFP64[10*10] [CX3011-1]	
STM8S208R6@LQFP64[14*14] [CX3044-1]	
STM8S208R8@LQFP64[10*10] [CX3011-1]	
STM8S208R8@LQFP64[14*14] [CX3044-1]	
STM8S208RB@LQFP64[10*10] [CX3011-1]	
STM8S208RB@LQFP64[14*14] [CX3044-1]	
STM8S208S6@LQFP44 [CX3005-1]	STM8S208S8@LQFP44 [CX3005-1]
STM8S208SB@LQFP44 [CX3005-1]	STM8S903F3@SOP20 [CX1033-3]

STM8S903F3@TSSOP20 [CX1067-1]  
STM8S903K3@QFN32 [CX4015-1]  
STM8TL52F4@TSSOP20 [CX1067-4]  
STM8TL53C4@QFN48 [CX4021-2]  
STM8TL53G4@QFN28 [CX4083-3]  
ZPSD211R@TQFP44 [CX3003]  
ZPSD211RV@TQFP44 [CX3003]  
ZPSD301@TQFP44 [CX3003]  
ZPSD301L@TQFP44 [CX3003]  
ZPSD301R@TQFP44 [CX3003]  
ZPSD301RL@TQFP44 [CX3003]  
ZPSD301RV@TQFP44 [CX3003]  
ZPSD301V@TQFP44 [CX3003]  
ZPSD302@TQFP44 [CX3003]  
ZPSD302B@PLCC44(USA) [CX2044]  
ZPSD302L@TQFP44 [CX3003]  
ZPSD302R@TQFP44 [CX3003]  
ZPSD302RL@TQFP44 [CX3003]  
ZPSD302RV@TQFP44 [CX3003]  
ZPSD302V@TQFP44 [CX3003]  
ZPSD303@TQFP44 [CX3003]  
ZPSD303L@TQFP44 [CX3003]  
ZPSD303R@TQFP44 [CX3003]  
ZPSD303RL@TQFP44 [CX3003]  
ZPSD303RV@TQFP44 [CX3003]  
ZPSD303V@TQFP44 [CX3003]  
ZPSD311@TQFP44 [CX3003]  
ZPSD311L@TQFP44 [CX3003]  
ZPSD311R@TQFP44 [CX3003]  
ZPSD311RL@TQFP44 [CX3003]  
ZPSD311RV@TQFP44 [CX3003]  
ZPSD311V@TQFP44 [CX3003]  
ZPSD312@TQFP44 [CX3046]  
ZPSD312L@PLCC44 [CX2044]  
ZPSD312R@PLCC44 [CX2044]  
ZPSD312RL@PLCC44 [CX2044]  
ZPSD312RV@PLCC44 [CX2044]  
ZPSD312V@PLCC44 [CX2044]  
ZPSD313@PLCC44 [CX2044]  
ZPSD313L@PLCC44 [CX2044]  
ZPSD313R@PLCC44 [CX2044]  
ZPSD313RL@PLCC44 [CX2044]  
ZPSD313RV@PLCC44 [CX2044]  
ZPSD313V@PLCC44 [CX2044]  
STM8S903K3@LQFP32 [CX3001-1]  
STM8S903K3@SDIP32 [CX0032-1]  
STM8TL52G4@QFN28 [CX4083-3]  
STM8TL53F4@TSSOP20 [CX1067-4]  
ZPSD211R@PLCC44 [CX2044]  
ZPSD211RV@PLCC44 [CX2044]  
ZPSD301@PLCC44 [CX2044]  
ZPSD301L@PLCC44 [CX2044]  
ZPSD301R@PLCC44 [CX2044]  
ZPSD301RL@PLCC44 [CX2044]  
ZPSD301RV@PLCC44 [CX2044]  
ZPSD301V@PLCC44 [CX2044]  
ZPSD302@PLCC44 [CX2044]  
ZPSD302B@PLCC44 [CX2044]  
ZPSD302L@PLCC44 [CX2044]  
ZPSD302R@PLCC44 [CX2044]  
ZPSD302RL@PLCC44 [CX2044]  
ZPSD302RV@PLCC44 [CX2044]  
ZPSD302V@PLCC44 [CX2044]  
ZPSD303@PLCC44 [CX2044]  
ZPSD303L@PLCC44 [CX2044]  
ZPSD303R@PLCC44 [CX2044]  
ZPSD303RL@PLCC44 [CX2044]  
ZPSD303RV@PLCC44 [CX2044]  
ZPSD303V@PLCC44 [CX2044]  
ZPSD311@PLCC44 [CX2044]  
ZPSD311L@PLCC44 [CX2044]  
ZPSD311R@PLCC44 [CX2044]  
ZPSD311RL@PLCC44 [CX2044]  
ZPSD311RV@PLCC44 [CX2044]  
ZPSD311V@PLCC44 [CX2044]  
ZPSD312@PLCC44 [CX2044]  
ZPSD312B@PLCC44 [CX2044]  
ZPSD312L@TQFP44 [CX3046]  
ZPSD312R@TQFP44 [CX3046]  
ZPSD312RL@TQFP44 [CX3046]  
ZPSD312RV@TQFP44 [CX3046]  
ZPSD312V@TQFP44 [CX3046]  
ZPSD313@TQFP44 [CX3003]  
ZPSD313L@TQFP44 [CX3003]  
ZPSD313R@TQFP44 [CX3003]  
ZPSD313RL@TQFP44 [CX3003]  
ZPSD313RV@TQFP44 [CX3003]  
ZPSD313V@TQFP44 [CX3003]

## STC

### MICROCONTROLLER

STC89C516RD [CX0001]  
STC89C516RD@TQFP44 [CX3003]  
STC89C58RD@PLCC44 [CX2044]  
STC89LE516AD [CX0001]  
STC89LE516AD@TQFP44 [CX3003]  
STC89LE516X2@PLCC44 [CX2044]  
STC89LE52AD [CX0001]  
STC89LE52AD@TQFP44 [CX3003]  
STC89LE54AD@PLCC44 [CX2044]  
STC89C516RD@PLCC44 [CX2044]  
STC89C58RD [CX0001]  
STC89C58RD@TQFP44 [CX3003]  
STC89LE516AD@PLCC44 [CX2044]  
STC89LE516X2 [CX0001]  
STC89LE516X2@TQFP44 [CX3003]  
STC89LE52AD@PLCC44 [CX2044]  
STC89LE54AD [CX0001]  
STC89LE54AD@TQFP44 [CX3003]

STC89LE556AD [CX0001]  
STC89LE556AD@TQFP44 [CX3003]  
STC89LE556X2@PLCC44 [CX2044]  
STC89LE58AD [CX0001]  
STC89LE58AD@TQFP44 [CX3003]  
STC89LV516RD@PLCC44 [CX2044]  
STC89LV58RD [CX0001]  
STC89LV58RD@TQFP44 [CX3003]

STC89LE556AD@PLCC44 [CX2044]  
STC89LE556X2 [CX0001]  
STC89LE556X2@TQFP44 [CX3003]  
STC89LE58AD@PLCC44 [CX2044]  
STC89LV516RD [CX0001]  
STC89LV516RD@TQFP44 [CX3003]  
STC89LV58RD@PLCC44 [CX2044]

## ST-CUSTOMER

### E (E) PROM/FRAM/NVRAM

NAND01GW3B2CN6 (MOTOROLA)@TSOP48 [CX1004-1]

## SULC

### E (E) PROM/FRAM/NVRAM

CF48F6300M0U0B (SPEC) [CX0051]  
CF48F6600M0U0B (SPEC) [CX0051]  
CF48F6600M0U0SF [CX0051]

CF48F6300M0U0BE [CX0051]  
CF48F6600M0U0BE [CX0051]  
CF48F6600M0U0SF (1G) [CX0051]

## SUMMIT

### E (E) PROM/FRAM/NVRAM

S24022 [CX0001]  
S24023 [CX0001]  
S24042 [CX0001]  
S24043 [CX0001]  
S24162 [CX0001]  
S24VP02 [CX0001]  
S24VP04 [CX0001]  
S24VP08 [CX0001]  
S24VP16 [CX0001]  
S93462 (08bit) [CX0001]  
S93462 (16bit) [CX0001]  
S93463 (08bit) [CX0001]  
S93463 (16bit) [CX0001]  
S93662 (08bit) [CX0001]  
S93662 (16bit) [CX0001]  
S93663 (08bit) [CX0001]  
S93663 (16bit) [CX0001]  
S93WD462 (08bit) [CX0001]  
S93WD462 (16bit) [CX0001]  
S93WD463 (08bit) [CX0001]  
S93WD463 (16bit) [CX0001]  
S93WD662 (08bit) [CX0001]  
S93WD662 (16bit) [CX0001]  
S93WD663 (08bit) [CX0001]  
S93WD663 (16bit) [CX0001]

S24022@SOIC8 [CX1045]  
S24023@SOIC8 [CX1045]  
S24042@SOIC8 [CX1045]  
S24043@SOIC8 [CX1045]  
S24162@SOIC8 [CX1045]  
S24VP02@SOIC8 [CX1045]  
S24VP04@SOIC8 [CX1045]  
S24VP08@SOIC8 [CX1045]  
S24VP16@SOIC8 [CX1045]  
S93462 (08bit)@SOIC8 [CX1045]  
S93462 (16bit)@SOIC8 [CX1045]  
S93463 (08bit)@SOIC8 [CX1045]  
S93463 (16bit)@SOIC8 [CX1045]  
S93662 (08bit)@SOIC8 [CX1045]  
S93662 (16bit)@SOIC8 [CX1045]  
S93663 (08bit)@SOIC8 [CX1045]  
S93663 (16bit)@SOIC8 [CX1045]  
S93WD462 (08bit)@SOIC8 [CX1045]  
S93WD462 (16bit)@SOIC8 [CX1045]  
S93WD463 (08bit)@SOIC8 [CX1045]  
S93WD463 (16bit)@SOIC8 [CX1045]  
S93WD662 (08bit)@SOIC8 [CX1045]  
S93WD662 (16bit)@SOIC8 [CX1045]  
S93WD663 (08bit)@SOIC8 [CX1045]  
S93WD663 (16bit)@SOIC8 [CX1045]

### MICROCONTROLLER

SMM465F-249@TQFP48 [CX3007]                   SMM465F-249@TQFP48(ISP) [CX0001]  
SMM665BFC-266@TQFP48 [CX3007]  
SMM665BFC-266@TQFP48(ISP) [CX0001]  
SMM665CFC-802@TQFP48 [CX3007]  
SMM665CFC-802@TQFP48(ISP) [CX0001]  
SMM766BF [CX3007]                               SMM766F [CX3007]

## SUNMOON

### E(E) PROM/FRAM/NVRAM

SM24C02 [CX0001]                               SM24C02@SOP8 [CX1045]  
SM24C04 [CX0001]                               SM24C04@SOP8 [CX1045]  
SM24C08 [CX0001]                               SM24C08@SOP8 [CX1045]  
SM24C16 [CX0001]                               SM24C16@SOP8 [CX1045]

## SUNPLUS

### MICROCONTROLLER

SPMC65P2102A(dip18) [CX0001]  
SPMC65P2102A(dip18)(ISP) [CX0001]  
SPMC65P2102A@SOP18 [CX1033]                SPMC65P2102A@SOP18(ISP) [CX0001]  
SPMC65P2104A(dip18) [CX0001]  
SPMC65P2104A(dip18)(ISP) [CX0001]  
SPMC65P2104A@SOP18 [CX1033]                SPMC65P2104A@SOP18(ISP) [CX0001]  
SPMC65P2202A(dip16) [CX0001]  
SPMC65P2202A(dip16)(ISP) [CX0001]  
SPMC65P2202A(dip20) [CX0001]  
SPMC65P2202A(dip20)(ISP) [CX0001]  
SPMC65P2202A@SOP16 [CX1033]                SPMC65P2202A@SOP16(ISP) [CX0001]  
SPMC65P2202A@SOP20 [CX1033]                SPMC65P2202A@SOP20(ISP) [CX0001]  
SPMC65P2204A(dip16) [CX0001]  
SPMC65P2204A(dip16)(ISP) [CX0001]  
SPMC65P2204A(dip20) [CX0001]  
SPMC65P2204A(dip20)(ISP) [CX0001]  
SPMC65P2204A@SOP16 [CX1033]                SPMC65P2204A@SOP16(ISP) [CX0001]  
SPMC65P2204A@SOP20 [CX1033]                SPMC65P2204A@SOP20(ISP) [CX0001]  
SPMC65P2404A(dip20) [CX0001]  
SPMC65P2404A(dip20)(ISP) [CX0001]  
SPMC65P2404A(dip28) [CX0001]  
SPMC65P2404A(dip28)(ISP) [CX0001]  
SPMC65P2404A@SOP20 [CX1033]                SPMC65P2404A@SOP20(ISP) [CX0001]  
SPMC65P2404A@SOP28 [CX1033]                SPMC65P2404A@SOP28(ISP) [CX0001]  
SPMC65P2408A(dip28) [CX0001]  
SPMC65P2408A(dip28)(ISP) [CX0001]  
SPMC65P2408A(dip32) [CX0001]  
SPMC65P2408A(dip32)(ISP) [CX0001]  
SPMC65P2408A@SOP28 [CX1033]                SPMC65P2408A@SOP28(ISP) [CX0001]  
SPMC65P2408A@SOP32 [CX1034]                SPMC65P2408A@SOP32(ISP) [CX0001]

## SYNCMOS

### E(E) PROM/FRAM/NVRAM

F29C31004B [CX0001]                           F29C31004B@PLCC32 [CX2032]

F29C31004B@TSOP32 [CX1002]  
F29C31004T@PLCC32 [CX2032]  
F29C51000B [CX0001]  
F29C51000B@TSOP32 [CX1002]  
F29C51000T@PLCC32 [CX2032]  
F29C51001B [CX0001]  
F29C51001B@TSOP32 [CX1002]  
F29C51001T@PLCC32 [CX2032]  
F29C51002B [CX0001]  
F29C51002B@TSOP32 [CX1002]  
F29C51002T@PLCC32 [CX2032]  
F29C51004B [CX0001]  
F29C51004B@TSOP32 [CX1002]  
F29C51004T@PLCC32 [CX2032]  
F29LC51000 [CX0001]  
F29LC51000@TSOP32 [CX1002]  
F29LC51001@PLCC32 [CX2032]  
F29LC51002 [CX0001]  
F29LC51002@TSOP32 [CX1002]  
S29C31001B@PLCC32 [CX2032]  
S29C31001T [CX0001]  
S29C31001T@TSOP32 [CX1002]  
S29C31002B@PLCC32 [CX2032]  
S29C31002T [CX0001]  
S29C31002T@TSOP32 [CX1002]  
S29C31004B@PLCC32 [CX2032]  
S29C31004T [CX0001]  
S29C31004T@TSOP32 [CX1002]  
S29C51001B@PLCC32 [CX2032]  
S29C51001T [CX0001]  
S29C51001T@TSOP32 [CX1002]  
S29C51002B@PLCC32 [CX2032]  
S29C51002T [CX0001]  
S29C51002T@TSOP32 [CX1002]  
S29C51004B@PLCC32 [CX2032]  
S29C51004T [CX0001]  
S29C51004T@TSOP32 [CX1002]

F29C31004T [CX0001]  
F29C31004T@TSOP32 [CX1002]  
F29C51000B@PLCC32 [CX2032]  
F29C51000T [CX0001]  
F29C51000T@TSOP32 [CX1002]  
F29C51001B@PLCC32 [CX2032]  
F29C51001T [CX0001]  
F29C51001T@TSOP32 [CX1002]  
F29C51002B@PLCC32 [CX2032]  
F29C51002T [CX0001]  
F29C51002T@TSOP32 [CX1002]  
F29C51004B@PLCC32 [CX2032]  
F29C51004T [CX0001]  
F29C51004T@TSOP32 [CX1002]  
F29LC51000@PLCC32 [CX2032]  
F29LC51001 [CX0001]  
F29LC51001@TSOP32 [CX1002]  
F29LC51002@PLCC32 [CX2032]  
S29C31001B [CX0001]  
S29C31001B@TSOP32 [CX1002]  
S29C31001T@PLCC32 [CX2032]  
S29C31002B [CX0001]  
S29C31002B@TSOP32 [CX1002]  
S29C31002T@PLCC32 [CX2032]  
S29C31004B [CX0001]  
S29C31004B@TSOP32 [CX1002]  
S29C31004T@PLCC32 [CX2032]  
S29C51001B [CX0001]  
S29C51001B@TSOP32 [CX1002]  
S29C51001T@PLCC32 [CX2032]  
S29C51002B [CX0001]  
S29C51002B@TSOP32 [CX1002]  
S29C51002T@PLCC32 [CX2032]  
S29C51004B [CX0001]  
S29C51004B@TSOP32 [CX1002]  
S29C51004T@PLCC32 [CX2032]

## MICROCONTROLLER

MSU1958 [CX0001]  
MSU1958@TQFP44 [CX3002]  
MSU2952@PLCC44 [CX2044]  
MSU2964 [CX0001]  
MSU2964@TQFP44 [CX3002]  
SM2958@PLCC44 [CX2044]  
SM2965 [CX0001]  
SM2965@TQFP44 [CX3002]  
SM39R02G1@DIP14 [CX0001]  
SM39R02G1@SOP14 [CX1016]  
SM39R04G1@DIP14 [CX0001]  
SM39R04G1@SOP14 [CX1016]  
SM39R05A3@DIP14 [CX0001]  
SM39R05A3@DIP20 [CX0001]  
SM39R05A3@SOP14 [CX1016]  
SM39R05A3@SOP20 [CX1033]  
SM39R05A5@DIP10 [CX0001]  
SM39R05A5@SOP10 [CX1051]  
SM39R08A2(dip16) [CX0001]

MSU1958@PLCC44 [CX2044]  
MSU2952 [CX0001]  
MSU2952@TQFP44 [CX3002]  
MSU2964@PLCC44 [CX2044]  
SM2958 [CX0001]  
SM2958@TQFP44 [CX3002]  
SM2965@PLCC44 [CX2044]  
SM39R02G1@DIP10 [CX0001]  
SM39R02G1@MSOP10 [CX1051]  
SM39R04G1@DIP10 [CX0001]  
SM39R04G1@MSOP10 [CX1051]  
SM39R05A3@DIP10 [CX0001]  
SM39R05A3@DIP16 [CX0001]  
SM39R05A3@SOP10 [CX1051]  
SM39R05A3@SOP16 [CX1016]  
SM39R05A3@SSOP20 [CX1025]  
SM39R05A5@DIP8 [CX0001]  
SM39R05A5@SOP8 [CX1051]  
SM39R08A2(dip20) [CX0001]

SM39R08A2(dip24) [CX0001]	SM39R08A2(dip28) [CX0001]
SM39R08A2@PLCC28 [CX2028]	SM39R08A2@SOP16 [CX1033]
SM39R08A2@SOP20 [CX1033]	SM39R08A2@SOP24 [CX1033]
SM39R08A2@SOP28 [CX1033]	SM39R08A3@DIP10 [CX0001]
SM39R08A3@DIP14 [CX0001]	SM39R08A3@DIP16 [CX0001]
SM39R08A3@DIP20 [CX0001]	SM39R08A3@SOP10 [CX1051]
SM39R08A3@SOP14 [CX1016]	SM39R08A3@SOP16 [CX1016]
SM39R08A3@SOP20 [CX1033]	SM39R08A3@SSOP20 [CX1025]
SM39R08A5@DIP10 [CX0001]	SM39R08A5@DIP8 [CX0001]
SM39R08A5@SOP10 [CX1051]	SM39R08A5@SOP8 [CX1051]
SM39R12A2(dip16) [CX0001]	SM39R12A2(dip20) [CX0001]
SM39R12A2(dip24) [CX0001]	SM39R12A2(dip28) [CX0001]
SM39R12A2@PLCC28 [CX2028]	SM39R12A2@SOP16 [CX1033]
SM39R12A2@SOP20 [CX1033]	SM39R12A2@SOP24 [CX1033]
SM39R12A2@SOP28 [CX1033]	SM39R16A2(dip16) [CX0001]
SM39R16A2(dip20) [CX0001]	SM39R16A2(dip24) [CX0001]
SM39R16A2(dip28) [CX0001]	SM39R16A2@PLCC28 [CX2028]
SM39R16A2@SOP16 [CX1033]	SM39R16A2@SOP20 [CX1033]
SM39R16A2@SOP24 [CX1033]	SM39R16A2@SOP28 [CX1033]
SM39R16A3@DIP10 [CX0001]	SM39R16A3@DIP14 [CX0001]
SM39R16A3@DIP16 [CX0001]	SM39R16A3@DIP20 [CX0001]
SM39R16A3@DIP28 [CX0001]	SM39R16A3@LQFP32 [CX3001]
SM39R16A3@SOP10 [CX1051]	SM39R16A3@SOP14 [CX1016]
SM39R16A3@SOP16 [CX1016]	SM39R16A3@SOP20 [CX1033]
SM39R16A3@SOP28 [CX1033]	SM39R16A3@SSOP20 [CX1025]
SM39R2051 [CX0001]	SM39R2051@SOP20 [CX1033]
SM39R4051 [CX0001]	SM39R4051@SOP20 [CX1033]
SM59064 [CX0001]	SM59064@PLCC44 [CX2044]
SM59064@TQFP44 [CX3002]	SM59128C [CX0001]
SM59128C@PLCC44 [CX2044]	SM59128C@TQFP44 [CX3002]
SM59128L [CX0001]	SM59128L@PLCC44 [CX2044]
SM59128L@TQFP44 [CX3002]	SM5912C [CX0001]
SM5912C(ISP) [CX0001]	SM5912C@PLCC44 [CX2044]
SM5912C@PLCC44(ISP) [CX0001]	SM5912C@TQFP44 [CX3002]
SM5912C@TQFP44(ISP) [CX0001]	SM5912L [CX0001]
SM5912L(ISP) [CX0001]	SM5912L@PLCC44 [CX2044]
SM5912L@PLCC44(ISP) [CX0001]	SM5912L@TQFP44 [CX3002]
SM5912L@TQFP44(ISP) [CX0001]	SM59164 [CX0001]
SM59164@PLCC44 [CX2044]	SM59164@TQFP44 [CX3002]
SM5916C [CX0001]	SM5916C(ISP) [CX0001]
SM5916C@PLCC44 [CX2044]	SM5916C@PLCC44(ISP) [CX0001]
SM5916C@TQFP44 [CX3002]	SM5916C@TQFP44(ISP) [CX0001]
SM5916L [CX0001]	SM5916L(ISP) [CX0001]
SM5916L@PLCC44 [CX2044]	SM5916L@PLCC44(ISP) [CX0001]
SM5916L@TQFP44 [CX3002]	SM5916L@TQFP44(ISP) [CX0001]
SM59264 [CX0001]	SM59264@PLCC44 [CX2044]
SM59264@TQFP44 [CX3002]	SM5964 [CX0001]
SM5964@PLCC44 [CX2044]	SM5964@TQFP44 [CX3002]
SM5964A [CX0001]	SM5964A@PLCC44 [CX2044]
SM5964A@TQFP44 [CX3002]	SM5964AC [CX0001]
SM5964AC@PLCC44 [CX2044]	SM5964AC@TQFP44 [CX3002]
SM5964AL [CX0001]	SM5964AL@PLCC44 [CX2044]
SM5964AL@TQFP44 [CX3002]	SM5964C [CX0001]
SM5964C@PLCC44 [CX2044]	SM5964C@TQFP44 [CX3002]
SM5964D0 [CX0001]	SM5964D0@PLCC44 [CX2044]
SM5964D0@TQFP44 [CX3002]	SM5964D0A [CX0001]
SM5964D0A@PLCC44 [CX2044]	SM5964D0A@TQFP44 [CX3002]
SM5964D1A [CX0001]	SM5964D1A@PLCC44 [CX2044]
SM5964D1A@TQFP44 [CX3002]	SM59A16U1 [CX0001]

SM59A16U1@LQFP44 [CX3002]  
SM59A16U1@LQFP64 [CX3011]  
SM59D02G2C(ISP) [CX0001]  
SM59D02G2C@PLCC44(ISP) [CX0001]  
SM59D02G2C@TQFP44(ISP) [CX0001]  
SM59D02G2L(ISP) [CX0001]  
SM59D02G2L@PLCC44(ISP) [CX0001]  
SM59D02G2L@TQFP44(ISP) [CX0001]  
SM59D03G2C(ISP) [CX0001]  
SM59D03G2C@PLCC44(ISP) [CX0001]  
SM59D03G2C@TQFP44(ISP) [CX0001]  
SM59D03G2L(ISP) [CX0001]  
SM59D03G2L@PLCC44(ISP) [CX0001]  
SM59D03G2L@TQFP44(ISP) [CX0001]  
SM59D04G2C(ISP) [CX0001]  
SM59D04G2C@PLCC44(ISP) [CX0001]  
SM59D04G2C@TQFP44(ISP) [CX0001]  
SM59D04G2L(ISP) [CX0001]  
SM59D04G2L@PLCC44(ISP) [CX0001]  
SM59D04G2L@TQFP44(ISP) [CX0001]  
SM59R01G1@PLCC44 [CX2044]  
SM59R02A1C [CX0001]  
SM59R02A1C@PLCC44 [CX2044]  
SM59R02A1L [CX0001]  
SM59R02A1L@PLCC44 [CX2044]  
SM59R02G1 [CX0001]  
SM59R02G1@TQFP44 [CX3002]  
SM59R03A1C@LQFP48 [CX3007]  
SM59R03A1C@QFP44 [CX3002]  
SM59R03A1L@LQFP48 [CX3007]  
SM59R03A1L@QFP44 [CX3002]  
SM59R04A1C@LQFP48 [CX3007]  
SM59R04A1C@QFP44 [CX3002]  
SM59R04A1L@LQFP48 [CX3007]  
SM59R04A1L@QFP44 [CX3002]  
SM59R04A2C@LQFP48 [CX3007]  
SM59R04A2C@QFP44 [CX3002]  
SM59R04A2L@LQFP48 [CX3007]  
SM59R04A2L@QFP44 [CX3002]  
SM59R05A3C@LQFP48 [CX3007]  
SM59R05A3C@QFP44 [CX3002]  
SM59R05A3L@LQFP48 [CX3007]  
SM59R05A3L@QFP44 [CX3002]  
SM59R05A5C@LQFP48 [CX3007]  
SM59R05A5C@QFP44 [CX3002]  
SM59R05A5L@LQFP48 [CX3007]  
SM59R05A5L@QFP44 [CX3002]  
SM59R05G6W@LQFP48 [CX3007]  
SM59R05G6W@QFP44 [CX3002]  
SM59R09A3C [CX0001]  
SM59R09A3C@PLCC44 [CX2044]  
SM59R09A3L [CX0001]  
SM59R09A3L@PLCC44 [CX2044]  
SM59R09A5C [CX0001]  
SM59R09A5C@PLCC44 [CX2044]  
SM59R09A5L [CX0001]  
SM59R09A5L@PLCC44 [CX2044]  
SM59R09G6W [CX0001]  
SM59R09G6W@PLCC44 [CX2044]

SM59A16U1@LQFP48 [CX3007]  
SM59D02G2C [CX0001]  
SM59D02G2C@PLCC44 [CX2044]  
SM59D02G2C@TQFP44 [CX3002]  
SM59D02G2L [CX0001]  
SM59D02G2L@PLCC44 [CX2044]  
SM59D02G2L@TQFP44 [CX3002]  
SM59D03G2C [CX0001]  
SM59D03G2C@PLCC44 [CX2044]  
SM59D03G2C@TQFP44 [CX3002]  
SM59D03G2L [CX0001]  
SM59D03G2L@PLCC44 [CX2044]  
SM59D03G2L@TQFP44 [CX3002]  
SM59D04G2C [CX0001]  
SM59D04G2C@PLCC44 [CX2044]  
SM59D04G2C@TQFP44 [CX3002]  
SM59D04G2L [CX0001]  
SM59D04G2L@PLCC44 [CX2044]  
SM59D04G2L@TQFP44 [CX3002]  
SM59R01G1 [CX0001]  
SM59R01G1@TQFP44 [CX3002]  
SM59R02A1C@LQFP48 [CX3007]  
SM59R02A1C@QFP44 [CX3002]  
SM59R02A1L@LQFP48 [CX3007]  
SM59R02A1L@QFP44 [CX3002]  
SM59R02G1@PLCC44 [CX2044]  
SM59R03A1C [CX0001]  
SM59R03A1C@PLCC44 [CX2044]  
SM59R03A1L [CX0001]  
SM59R03A1L@PLCC44 [CX2044]  
SM59R04A1C [CX0001]  
SM59R04A1C@PLCC44 [CX2044]  
SM59R04A1L [CX0001]  
SM59R04A1L@PLCC44 [CX2044]  
SM59R04A2C [CX0001]  
SM59R04A2C@PLCC44 [CX2044]  
SM59R04A2L [CX0001]  
SM59R04A2L@PLCC44 [CX2044]  
SM59R05A3C [CX0001]  
SM59R05A3C@PLCC44 [CX2044]  
SM59R05A3L [CX0001]  
SM59R05A3L@PLCC44 [CX2044]  
SM59R05A5C [CX0001]  
SM59R05A5C@PLCC44 [CX2044]  
SM59R05A5L [CX0001]  
SM59R05A5L@PLCC44 [CX2044]  
SM59R05G6W [CX0001]  
SM59R05G6W@PLCC44 [CX2044]  
SM59R05G6W@TQFP64 [CX3011]  
SM59R09A3C@LQFP48 [CX3007]  
SM59R09A3C@QFP44 [CX3002]  
SM59R09A3L@LQFP48 [CX3007]  
SM59R09A3L@QFP44 [CX3002]  
SM59R09A5C@LQFP48 [CX3007]  
SM59R09A5C@QFP44 [CX3002]  
SM59R09A5L@LQFP48 [CX3007]  
SM59R09A5L@QFP44 [CX3002]  
SM59R09G6W@LQFP48 [CX3007]  
SM59R09G6W@QFP44 [CX3002]

SM59R09G6W@TQFP64 [CX3011]  
SM59R16A3C@LQFP48 [CX3007]  
SM59R16A3C@QFP44 [CX3002]  
SM59R16A3L@LQFP48 [CX3007]  
SM59R16A3L@QFP44 [CX3002]  
SM59R16A5C@LQFP48 [CX3007]  
SM59R16A5C@QFP44 [CX3002]  
SM59R16A5L@LQFP48 [CX3007]  
SM59R16A5L@QFP44 [CX3002]  
SM59R16G6W@LQFP48 [CX3007]  
SM59R16G6W@QFP44 [CX3002]  
SM7908 [CX0001]  
SM7908@TQFP44 [CX3002]  
SM79108@PLCC44 [CX2044]  
SM79164 [CX0001]  
SM79164@TQFP44 [CX3002]  
SM79164L@PLCC44 [CX2044]  
SM79164V [CX0001]  
SM79164V@TQFP44 [CX3002]  
SM7932@PLCC44 [CX2044]  
SM7964 [CX0001]  
SM7964@TQFP44 [CX3002]  
SM894051@SOIC20 [CX1031]  
SM8951@PLCC44 [CX2044]  
SM89516 [CX0001]  
SM89516@TQFP44 [CX3002]  
SM89516A@PLCC44 [CX2044]  
SM89516AL [CX0001]  
SM89516AL@TQFP44 [CX3002]  
SM89516B@PLCC44 [CX2044]  
SM89516BL [CX0001]  
SM89516BL@TQFP44 [CX3002]  
SM89516L@PLCC44 [CX2044]  
SM8951A [CX0001]  
SM8951A@TQFP44 [CX3002]  
SM8951AL@PLCC44 [CX2044]  
SM8951B [CX0001]  
SM8951B@TQFP44 [CX3002]  
SM8951BL@PLCC44 [CX2044]  
SM8951L [CX0001]  
SM8951L@TQFP44 [CX3002]  
SM8952@PLCC44 [CX2044]  
SM8952A [CX0001]  
SM8952A@TQFP44 [CX3002]  
SM8952AL@PLCC44 [CX2044]  
SM8952B [CX0001]  
SM8952B@TQFP44 [CX3002]  
SM8952BL@PLCC44 [CX2044]  
SM8952L [CX0001]  
SM8952L@TQFP44 [CX3002]  
SM8954@PLCC44 [CX2044]  
SM8954A [CX0001]  
SM8954A@TQFP44 [CX3002]  
SM8954AL@PLCC44 [CX2044]  
SM8954B [CX0001]  
SM8954B@TQFP44 [CX3002]  
SM8954BL@PLCC44 [CX2044]  
SM8954L [CX0001]  
SM8954L@TQFP44 [CX3002]  
SM59R16A3C [CX0001]  
SM59R16A3C@PLCC44 [CX2044]  
SM59R16A3L [CX0001]  
SM59R16A3L@PLCC44 [CX2044]  
SM59R16A5C [CX0001]  
SM59R16A5C@PLCC44 [CX2044]  
SM59R16A5L [CX0001]  
SM59R16A5L@PLCC44 [CX2044]  
SM59R16G6W [CX0001]  
SM59R16G6W@PLCC44 [CX2044]  
SM59R16G6W@TQFP64 [CX3011]  
SM7908@PLCC44 [CX2044]  
SM79108 [CX0001]  
SM79108@TQFP44 [CX3002]  
SM79164@PLCC44 [CX2044]  
SM79164L [CX0001]  
SM79164L@TQFP44 [CX3002]  
SM79164V@PLCC44 [CX2044]  
SM7932 [CX0001]  
SM7932@TQFP44 [CX3002]  
SM7964@PLCC44 [CX2044]  
SM894051 [CX0001]  
SM8951 [CX0001]  
SM8951@TQFP44 [CX3002]  
SM89516@PLCC44 [CX2044]  
SM89516A [CX0001]  
SM89516A@TQFP44 [CX3002]  
SM89516AL@PLCC44 [CX2044]  
SM89516B [CX0001]  
SM89516B@TQFP44 [CX3002]  
SM89516BL@PLCC44 [CX2044]  
SM89516L [CX0001]  
SM89516L@TQFP44 [CX3002]  
SM8951A@PLCC44 [CX2044]  
SM8951AL [CX0001]  
SM8951AL@TQFP44 [CX3002]  
SM8951B@PLCC44 [CX2044]  
SM8951BL [CX0001]  
SM8951BL@TQFP44 [CX3002]  
SM8951L@PLCC44 [CX2044]  
SM8952 [CX0001]  
SM8952@TQFP44 [CX3002]  
SM8952A@PLCC44 [CX2044]  
SM8952AL [CX0001]  
SM8952AL@TQFP44 [CX3002]  
SM8952B@PLCC44 [CX2044]  
SM8952BL [CX0001]  
SM8952BL@TQFP44 [CX3002]  
SM8952L@PLCC44 [CX2044]  
SM8954 [CX0001]  
SM8954@TQFP44 [CX3002]  
SM8954A@PLCC44 [CX2044]  
SM8954AL [CX0001]  
SM8954AL@TQFP44 [CX3002]  
SM8954B@PLCC44 [CX2044]  
SM8954BL [CX0001]  
SM8954BL@TQFP44 [CX3002]  
SM8954L@PLCC44 [CX2044]  
SM8958 [CX0001]



SM8958@PLCC44 [CX2044]  
SM8958A [CX0001]  
SM8958A@TQFP44 [CX3002]  
SM8958AL@PLCC44 [CX2044]  
SM8958B [CX0001]  
SM8958B@TQFP44 [CX3002]  
SM8958BL@PLCC44 [CX2044]  
SM8958L [CX0001]  
SM8958L@TQFP44 [CX3002]  
SM89S16R1C@PLCC44 [CX2044]  
SM89T04R1C [CX0001]  
SM89T04R1C@TQFP44 [CX3002]  
SM89T04R1L@PLCC44 [CX2044]  
SM89T08R1C [CX0001]  
SM89T08R1C@TQFP44 [CX3002]  
SM89T08R1L@PLCC44 [CX2044]  
SM89T16R1C [CX0001]  
SM89T16R1C@TQFP44 [CX3002]  
SM89T16R1L@PLCC44 [CX2044]

SM8958@TQFP44 [CX3002]  
SM8958A@PLCC44 [CX2044]  
SM8958AL [CX0001]  
SM8958AL@TQFP44 [CX3002]  
SM8958B@PLCC44 [CX2044]  
SM8958BL [CX0001]  
SM8958BL@TQFP44 [CX3002]  
SM8958L@PLCC44 [CX2044]  
SM89S16R1C [CX0001]  
SM89S16R1C@TQFP44 [CX3002]  
SM89T04R1C@PLCC44 [CX2044]  
SM89T04R1L [CX0001]  
SM89T04R1L@TQFP44 [CX3002]  
SM89T08R1C@PLCC44 [CX2044]  
SM89T08R1L [CX0001]  
SM89T08R1L@TQFP44 [CX3002]  
SM89T16R1C@PLCC44 [CX2044]  
SM89T16R1L [CX0001]  
SM89T16R1L@TQFP44 [CX3002]

## SYNERTEK

### E (E) PROM/FRAM/NVRAM

SY2716 [CX0001]

## SYNTEK

### MICROCONTROLLER

STK6031@LQFP48 [CX3007]  
STK6031@QFP44 [CX3002]  
STK6032@LQFP48 [CX3007]  
STK6032@QFP44 [CX3002]  
STK6033@LQFP48 [CX3007]  
STK6033@QFP44 [CX3002]

STK6031@PLCC44 [CX2044]  
STK6032 [CX0001]  
STK6032@PLCC44 [CX2044]  
STK6033 [CX0001]  
STK6033@PLCC44 [CX2044]

## SZXG

### MICROCONTROLLER

MB95F108AHSPFM [CX3012]  
MB95F108AHWPFM [CX3012]  
MB95F108AJSPFM [CX3012]  
MB95F108AJWPFM [CX3012]  
MB95F108AKSPFM [CX3012]  
MB95F108AKWPFM [CX3012]  
MB95F108AMSPFM [CX3012]  
MB95F108AMWPFM [CX3012]  
MB95F108ANSPFM [CX3012]  
MB95F108ANWPFM [CX3012]  
MB95F108ATSPFM [CX3012]  
MB95F108ATWPFM [CX3012]  
MB95F108BHSPFM [CX3012]  
MB95F108BHWPFM [CX3012]  
MB95F108BJSPPM [CX3012]

MB95F108AHSPFV [CX3011]  
MB95F108AHWPFV [CX3011]  
MB95F108AJSPFV [CX3012]  
MB95F108AJWPFV [CX3012]  
MB95F108AKSPFV [CX3011]  
MB95F108AKWPFV [CX3011]  
MB95F108AMSPFV [CX3011]  
MB95F108AMWPFV [CX3011]  
MB95F108ANSPFV [CX3012]  
MB95F108ANWPFV [CX3012]  
MB95F108ATSPFV [CX3011]  
MB95F108ATWPFV [CX3011]  
MB95F108BHSPFV [CX3011]  
MB95F108BHWPFV [CX3011]  
MB95F108BJSPPV [CX3012]

MB95F108BJWPFM [CX3012]  
MB95F108BKSPFM [CX3012]  
MB95F108BKWPFM [CX3012]  
MB95F108BMSPFM [CX3012]  
MB95F108BMWPFM [CX3012]  
MB95F108BNSPFM [CX3012]  
MB95F108BNWPFM [CX3012]  
MB95F108BTSPFM [CX3012]  
MB95F108BTWPFM [CX3012]

MB95F108BJWPFV [CX3012]  
MB95F108BKSPFV [CX3011]  
MB95F108BKWPFV [CX3011]  
MB95F108BMSPFV [CX3011]  
MB95F108BMWPFV [CX3011]  
MB95F108BNSPFV [CX3012]  
MB95F108BNWPFV [CX3012]  
MB95F108BTSPFV [CX3011]  
MB95F108BTWPFV [CX3011]

## TECHCODE

### MICROCONTROLLER

T89C516 [CX0001]  
T89C516@TQFP44 [CX3002]  
T89C52@PLCC44 [CX2044]  
T89C58 [CX0001]  
T89C58@TQFP44 [CX3002]

T89C516@PLCC44 [CX2044]  
T89C52 [CX0001]  
T89C52@TQFP44 [CX3002]  
T89C58@PLCC44 [CX2044]

## TEKMOS

### MICROCONTROLLER

TK87C751 [CX0001]

TK87C751@PLCC28 [CX2028]

## TEMIC

### MICROCONTROLLER

T89C51RD2 [CX0001]  
T89C51RD2@TQFP44 [CX3003]  
T89F64@PLCC44 [CX2044]  
TS87C51RB2 [CX0001]  
TS87C51RB2@TQFP44 [CX3002]  
TS87C51RC2@PLCC44 [CX2044]  
TS87C51RD2 [CX0001]  
TS87C51RD2@TQFP44 [CX3002]  
TS87C51U2@PLCC44 [CX2044]  
TS87C52X2 [CX0001]  
TS87C52X2@TQFP44 [CX3002]  
TS87C54X2@PLCC44 [CX2044]  
TS87C58X2 [CX0001]  
TS87C58X2@TQFP44 [CX3002]  
TSC71RBX2@PLCC44 [CX2044]  
TSC71RCX2 [CX0001]  
TSC71RCX2@TQFP44 [CX3002]  
TSC71RDX2@PLCC44 [CX2044]  
TSC71RDX2@TQFP44 [CX3002]  
TSC87251A1@PLCC44 [CX2044]  
TSC87251G1@PLCC44 [CX2004]  
TSC87251G1A@PLCC44 [CX2044]  
TSC87251G2D@PLCC44 [CX2044]  
TSC87C51 [CX0001]  
TSC87C51@TQFP44 [CX3002]  
TSC87C52@PLCC44 [CX2044]

T89C51RD2@PLCC44 [CX2044]  
T89F64 [CX0001]  
T89F64@TQFP44 [CX3003]  
TS87C51RB2@PLCC44 [CX2044]  
TS87C51RC2 [CX0001]  
TS87C51RC2@TQFP44 [CX3002]  
TS87C51RD2@PLCC44 [CX2044]  
TS87C51U2 [CX0001]  
TS87C51U2@TQFP44 [CX3002]  
TS87C52X2@PLCC44 [CX2044]  
TS87C54X2 [CX0001]  
TS87C54X2@TQFP44 [CX3002]  
TS87C58X2@PLCC44 [CX2044]  
TSC71RBX2 [CX0001]  
TSC71RBX2@TQFP44 [CX3002]  
TSC71RCX2@PLCC44 [CX2044]  
TSC71RDX2 [CX0001]  
TSC71RDX2@PLCC68 [CX2068]  
TSC71RDX2@TQFP64 [CX3012]  
TSC87251G1 [CX0001]  
TSC87251G1A [CX0001]  
TSC87251G2D [CX0001]  
TSC87251G2D@TQFP44 [CX3003]  
TSC87C51@PLCC44 [CX2044]  
TSC87C52 [CX0001]  
TSC87C52@TQFP44 [CX3002]

TSC87C54 [CX0001]  
TSC87C54@TQFP44 [CX3002]  
TSC87C58@PLCC44 [CX2044]

TSC87C54@PLCC44 [CX2044]  
TSC87C58 [CX0001]  
TSC87C58@TQFP44 [CX3002]

## TERIDIAN

### MICROCONTROLLER

71M6513H-IGT [CX3021-7]  
71M6513-IGT [CX3021-7]  
71M6521BE-IGT [CX3011-13]  
71M6521DE-IGT [CX3011-13]  
71M6521FE-IGT [CX3011-13]

71M6513H-IGTR [CX3021-7]  
71M6513-IGTR [CX3021-7]  
71M6521BE-IM [CX4026-1]  
71M6521DE-IM [CX4026-1]  
71M6521FE-IM [CX4026-1]

## Terra Semiconductor

### E (E) PROM/FRAM/NVRAM

TS25L010AP [CX1044#1]  
TS25L020AP [CX1044#1]  
TS25L16AP [CX1044#1]  
TS25L16BP@SOP8 [CX1044#1]  
TS25L80AP@SOP8 [CX1044#1]

TS25L010AP@SOP8 [CX1044#1]  
TS25L020AP@SOP8 [CX1044#1]  
TS25L16AP@SOP8 [CX1044#1]  
TS25L80AP [CX1044#1]

## TI

### E (E) PROM/FRAM/NVRAM

BQ3285 [CX0001]  
BQ3287A [CX0001]  
BQ4010Y [CX0001]  
BQ4011Y [CX0001]  
BQ4013Y [CX0001]  
BQ4014Y [CX0001]  
BQ4015Y [CX0001]  
SMJ2532 [CX0001]  
SMJ2716 [CX0001]  
SMJ27C256@PLCC32 [CX2032]  
SMJ27C512@PLCC32 [CX2032]  
TMS2516JLW [CX0001]  
TMS2532A [CX0001]  
TMS27128 [CX0001]  
TMS2716 [CX0001]  
TMS2732A [CX0001]  
TMS27C010 [CX0001]  
TMS27C010@TSOP32 [CX1002]  
TMS27C010A@PLCC32 [CX2032]  
TMS27C020 [CX0001]  
TMS27C020@TSOP32 [CX1002]  
TMS27C040@PLCC32 [CX2032]  
TMS27C128 [CX0001]  
TMS27C2001 [CX0001]  
TMS27C2001@TSOP32 [CX1002]  
TMS27C210@PLCC44 [CX2044]  
TMS27C210A@PLCC44 [CX2044]  
TMS27C240@PLCC44 [CX2044]

BQ3287 [CX0001]  
BQ4010 [CX0001]  
BQ4011 [CX0001]  
BQ4013 [CX0001]  
BQ4014 [CX0001]  
BQ4015 [CX0001]  
SMJ2516 [CX0001]  
SMJ2532A [CX0001]  
SMJ27C256 [CX0001]  
SMJ27C512 [CX0001]  
TMS2516 [CX0001]  
TMS2532 [CX0001]  
TMS25L32 [CX0001]  
TMS27128A [CX0001]  
TMS2732 [CX0001]  
TMS2764 [CX0001]  
TMS27C010@PLCC32 [CX2032]  
TMS27C010A [CX0001]  
TMS27C010A@TSOP32 [CX1002]  
TMS27C020@PLCC32 [CX2032]  
TMS27C040 [CX0001]  
TMS27C040@TSOP32 [CX1002]  
TMS27C128@PLCC32  
TMS27C2001@PLCC32 [CX2032]  
TMS27C210 [CX0001]  
TMS27C210A [CX0001]  
TMS27C240 [CX0001]  
TMS27C256 [CX0001]

TMS27C256@PLCC32 [CX2032]  
TMS27C291@PLCC28 [CX2028]  
TMS27C292@PLCC28 [CX2028]  
TMS27C512 [CX0001]  
TMS27C64 [CX0001]  
TMS27LV010A@PLCC32 [CX2032]  
TMS27P32A [CX0001]  
TMS27PC010 [CX0001]  
TMS27PC010@TSOP32 [CX1002]  
TMS27PC010A@PLCC32 [CX2032]  
TMS27PC020 [CX0001]  
TMS27PC020@TSOP32 [CX1002]  
TMS27PC040@PLCC32 [CX2032]  
TMS27PC128 [CX0001]  
TMS27PC210 [CX0001]  
TMS27PC210A [CX0001]  
TMS27PC240 [CX0001]  
TMS27PC256 [CX0001]  
TMS27PC291 [CX0001]  
TMS27PC32 [CX0001]  
TMS27PC512 [CX0001]  
TMS27PC64 [CX0001]  
TMS28F010(REVERSE)@TSOP32 [CX1002]  
TMS28F010@PLCC32 [CX2032]  
TMS28F020 [CX0001]  
TMS28F020(REVERSE)@TSOP32 [CX1002]  
TMS28F020@PLCC32 [CX2032]  
TMS28F200AF-B@PSOP44 [CX1014]  
TMS28F200AF-T@PSOP44 [CX1014]  
TMS28F200BZ-B@PSOP44 [CX1014]  
TMS28F210 [CX0001]  
TMS28F210@TSOP40 [CX1005]  
TMS28F400AE-B@TSOP48 [CX1004]  
TMS28F400AE-T@TSOP48 [CX1004]  
TMS28F400AF-B@TSOP48 [CX1004]  
TMS28F400AF-T@TSOP48 [CX1004]  
TMS28F400AM-B@TSOP48 [CX1004]  
TMS28F400AM-T@TSOP48 [CX1004]  
TMS28F400AS-B@TSOP48 [CX1004]  
TMS28F400AS-T@TSOP48 [CX1004]  
TMS28F400AZ-B@TSOP48 [CX1004]  
TMS28F400AZ-T@TSOP48 [CX1004]  
TMS28F400BZ-B@PSOP44 [CX1014]  
TMS28F512(REVERSE)@TSOP32 [CX1002]  
TMS28F512@PLCC32 [CX2032]  
TMS28F800AE-B@PSOP44 [CX1014]  
TMS28F800AE-T@PSOP44 [CX1014]  
TMS28F800AL-B@PSOP44 [CX1014]  
TMS28F800AL-T@PSOP44 [CX1014]  
TMS28F800AS-B@PSOP44 [CX1014]  
TMS28F800AS-T@PSOP44 [CX1014]  
TMS28F800AV-B@PSOP44 [CX1014]  
TMS28F800AV-T@PSOP44 [CX1014]  
TMS28F800AZ-B@PSOP44 [CX1014]  
TMS28F800AZ-T@PSOP44 [CX1014]  
TMS28F800SE-B@PSOP44 [CX1014]  
TMS28F800SE-T@PSOP44 [CX1014]  
TMS28F800SZ-B@PSOP44 [CX1014]  
TMS28F800SZ-T@PSOP44 [CX1014]

TMS27C291 [CX0001]  
TMS27C292 [CX0001]  
TMS27C32 [CX0001]  
TMS27C512@PLCC32 [CX2032]  
TMS27LV010A [CX0001]  
TMS27LV010A@TSOP32 [CX1002]  
TMS27P64 [CX0001]  
TMS27PC010@PLCC32 [CX2032]  
TMS27PC010A [CX0001]  
TMS27PC010A@TSOP32 [CX1002]  
TMS27PC020@PLCC32 [CX2032]  
TMS27PC040 [CX0001]  
TMS27PC040@TSOP32 [CX1002]  
TMS27PC128@PLCC32  
TMS27PC210@PLCC44 [CX2044]  
TMS27PC210A@PLCC44 [CX2044]  
TMS27PC240@PLCC44 [CX2044]  
TMS27PC256@PLCC32 [CX2032]  
TMS27PC291@PLCC28 [CX2028]  
TMS27PC32A [CX0001]  
TMS27PC512@PLCC32 [CX2032]  
TMS28F010 [CX0001]  
TMS28F010@TSOP32 [CX1002]  
TMS28F020@TSOP32 [CX1002]  
TMS28F200AF-B@TSOP48 [CX1004]  
TMS28F200AF-T@TSOP48 [CX1004]  
TMS28F200BZ-T@PSOP44 [CX1014]  
TMS28F210@PLCC44 [CX2044]  
TMS28F400AE-B@PSOP44 [CX1014]  
TMS28F400AE-T@PSOP44 [CX1014]  
TMS28F400AF-B@PSOP44 [CX1014]  
TMS28F400AF-T@PSOP44 [CX1014]  
TMS28F400AM-B@PSOP44 [CX1014]  
TMS28F400AM-T@PSOP44 [CX1014]  
TMS28F400AS-B@PSOP44 [CX1014]  
TMS28F400AS-T@PSOP44 [CX1014]  
TMS28F400AZ-B@PSOP44 [CX1014]  
TMS28F400AZ-T@PSOP44 [CX1014]  
TMS28F400BZ-B@PSOP44 [CX1014]  
TMS28F512 [CX0001]  
TMS28F512@TSOP32 [CX1002]  
TMS28F800AE-B@TSOP48 [CX1004]  
TMS28F800AE-T@TSOP48 [CX1004]  
TMS28F800AL-B@TSOP48 [CX1004]  
TMS28F800AL-T@TSOP48 [CX1004]  
TMS28F800AS-B@TSOP48 [CX1004]  
TMS28F800AS-T@TSOP48 [CX1004]  
TMS28F800AV-B@TSOP48 [CX1004]  
TMS28F800AV-T@TSOP48 [CX1004]  
TMS28F800AZ-B@TSOP48 [CX1004]  
TMS28F800AZ-T@TSOP48 [CX1004]  
TMS28F800SE-B@TSOP48 [CX1004]  
TMS28F800SE-T@TSOP48 [CX1004]  
TMS28F800SZ-B@TSOP48 [CX1004]  
TMS28F800SZ-T@TSOP48 [CX1004]

TMS29F040 [CX0001]  
TMS29F040@TSOP32 [CX1002]  
TMS87C257@PLCC32 [CX2032]

TMS29F040@PLCC32 [CX2032]  
TMS87C257 [CX0001]

## BPROM

TBP28L42N [CX0001]  
TBP28S42 [CX0001]

TBP28P42 [CX0001]  
TBP28SA42 [CX0001]

## PLD

EP1800@PLCC68 [CX2068]  
EP1830@PLCC68 [CX2068]  
EP330@PLCC20 [CX2020]  
EP910@PLCC44 [CX2044]  
PAL16L8A@PLCC20 [CX2020]  
PAL16L8A-2@PLCC20 [CX2020]  
PAL16R4A@PLCC20 [CX2020]  
PAL16R4A-2@PLCC20 [CX2020]  
PAL16R6A@PLCC20 [CX2020]  
PAL16R6A-2@PLCC20 [CX2020]  
PAL16R8A@PLCC20 [CX2020]  
PAL16R8A-2@PLCC20 [CX2020]  
TIB82S167A@PLCC28 [CX2028]  
TIB82S167B@PLCC28 [CX2028]  
TIBPAL16L8-12@PLCC20 [CX2020]  
TIBPAL16L8-15@PLCC20 [CX2020]  
TIBPAL16L8-25@PLCC20 [CX2020]  
TIBPAL16R4-12@PLCC20 [CX2020]  
TIBPAL16R4-15@PLCC20 [CX2020]  
TIBPAL16R4-25@PLCC20 [CX2020]  
TIBPAL16R6-12@PLCC20 [CX2020]  
TIBPAL16R6-15@PLCC20 [CX2020]  
TIBPAL16R6-25@PLCC20 [CX2020]  
TIBPAL16R8-12@PLCC20 [CX2020]  
TIBPAL16R8-15@PLCC20 [CX2020]  
TIBPAL16R8-25@PLCC20 [CX2020]  
TIBPAL20L8-10@PLCC28 [CX2028]  
TIBPAL20L8-15@PLCC28 [CX2028]  
TIBPAL20L8-25@PLCC28 [CX2028]  
TIBPAL20L8-5@PLCC28 [CX2028]  
TIBPAL20L8-7@PLCC28 [CX2028]  
TIBPAL20R4-10@PLCC28 [CX2028]  
TIBPAL20R4-15@PLCC28 [CX2028]  
TIBPAL20R4-25@PLCC28 [CX2028]  
TIBPAL20R4-5@PLCC28 [CX2028]  
TIBPAL20R4-7@PLCC28 [CX2028]  
TIBPAL20R6-10@PLCC28 [CX2028]  
TIBPAL20R6-15@PLCC28 [CX2028]  
TIBPAL20R6-25@PLCC28 [CX2028]  
TIBPAL20R6-5@PLCC28 [CX2028]  
TIBPAL20R6-7@PLCC28 [CX2028]  
TIBPAL20R8-10@PLCC28 [CX2028]  
TIBPAL20R8-15@PLCC28 [CX2028]  
TIBPAL20R8-25@PLCC28 [CX2028]  
TIBPAL20R8-5@PLCC28 [CX2028]  
TIBPAL20R8-7@PLCC28 [CX2028]  
TIBPAL22V10@PLCC28 [CX2028]

EP1810@PLCC68 [CX2068]  
EP330 [CX0001]  
EP910 [CX0001]  
PAL16L8A [CX0001]  
PAL16L8A-2 [CX0001]  
PAL16R4A [CX0001]  
PAL16R4A-2 [CX0001]  
PAL16R6A [CX0001]  
PAL16R6A-2 [CX0001]  
PAL16R8A [CX0001]  
PAL16R8A-2 [CX0001]  
TIB82S167A [CX0001]  
TIB82S167B [CX0001]  
TIBPAL16L8-12 [CX0001]  
TIBPAL16L8-15 [CX0001]  
TIBPAL16L8-25 [CX0001]  
TIBPAL16R4-12 [CX0001]  
TIBPAL16R4-15 [CX0001]  
TIBPAL16R4-25 [CX0001]  
TIBPAL16R6-12 [CX0001]  
TIBPAL16R6-15 [CX0001]  
TIBPAL16R6-25 [CX0001]  
TIBPAL16R8-12 [CX0001]  
TIBPAL16R8-15 [CX0001]  
TIBPAL16R8-25 [CX0001]  
TIBPAL20L8-10 [CX0001]  
TIBPAL20L8-15 [CX0001]  
TIBPAL20L8-25 [CX0001]  
TIBPAL20L8-5 [CX0001]  
TIBPAL20L8-7 [CX0001]  
TIBPAL20R4-10 [CX0001]  
TIBPAL20R4-15 [CX0001]  
TIBPAL20R4-25 [CX0001]  
TIBPAL20R4-5 [CX0001]  
TIBPAL20R4-7 [CX0001]  
TIBPAL20R6-10 [CX0001]  
TIBPAL20R6-15 [CX0001]  
TIBPAL20R6-25 [CX0001]  
TIBPAL20R6-5 [CX0001]  
TIBPAL20R6-7 [CX0001]  
TIBPAL20R8-10 [CX0001]  
TIBPAL20R8-15 [CX0001]  
TIBPAL20R8-25 [CX0001]  
TIBPAL20R8-5 [CX0001]  
TIBPAL20R8-7 [CX0001]  
TIBPAL22V10 [CX0001]  
TIBPAL22V10-10 [CX0001]

TIBPAL22V10-10@PLCC28 [CX2028]      TIBPAL22V10-15 [CX0001]  
TIBPAL22V10-15@PLCC28 [CX2028]      TIBPAL22V10-20 [CX0001]  
TIBPAL22V10-20@PLCC28 [CX2028]      TIBPAL22V10-5 [CX0001]  
TIBPAL22V10-5@PLCC28 [CX2028]      TIBPAL22V10-7 [CX0001]  
TIBPAL22V10-7@PLCC28 [CX2028]      TIBPAL22V10A [CX0001]  
TIBPAL22V10A@PLCC28 [CX2028]      TICPAL22V10Z(0 PWR) [CX0001]  
TICPAL22V10Z(0 PWR)@PLCC28 [CX2028]  
TICPAL22V10Z(TURBO) [CX0001]  
TICPAL22V10Z(TURBO)@PLCC28 [CX2028]

## MICROCONTROLLER

BQ2022ADBZR [CX1041]      BQ2022ALPR [CX0001]  
BQ2022DBZR [CX1041]      BQ2022LPR [CX0001]  
BUF01900@DFN10 [CX4007]      BUF01900@TSSOP8 [CX1001]  
BUF01901@DFN10 [CX4007]      BUF01901@TSSOP8 [CX1001]  
BUF08630@QFN20 [CX4025]      BUF08821@SSOP20 [CX1001]  
BUF16820@SSOP32 [CX1027]      BUF20820@SSOP38 [CX1012]  
BUF22821@SSOP38 [CX1012]      CC430F5123IRGZ [CX4021]  
CC430F5125IRGZ [CX4021]      CC430F5127IRGZ [CX4021]  
CC430F5133IRGZ [CX4021]      CC430F5135IRGZ [CX4021]  
CC430F5137IRGZ [CX4021]      CC430F5143IRGZ [CX4021]  
CC430F5145IRGZ [CX4021]      CC430F5147IRGZ [CX4021]  
CC430F6125IRGC [CX4023]      CC430F6126IRGC [CX4023]  
CC430F6127IRGC [CX4023]      CC430F6135IRGC [CX4023]  
CC430F6137IRGC [CX4023]      CC430F6143IRGC [CX4023]  
CC430F6145IRGC [CX4023]      CC430F6147IRGC [CX4023]  
CDCE62005@QFN48 [CX4021]      LM3S5P36@LQFP64 [CX3011]  
LM4F110B2QR@LQFP64 [CX3057-9]      LM4F110C4QR@LQFP64 [CX3057-9]  
LM4F110E5QR@LQFP64 [CX3057-9]      LM4F110H5QR@LQFP64 [CX3057-9]  
LM4F111B2QR@LQFP64 [CX3057-9]      LM4F111C4QR@LQFP64 [CX3057-9]  
LM4F111E5QR@LQFP64 [CX3057-9]      LM4F111H5QR@LQFP64 [CX3057-9]  
LM4F120B2QR@LQFP64 [CX3057-9]      LM4F120C4QR@LQFP64 [CX3057-9]  
LM4F120E5QR@LQFP64 [CX3057-9]      LM4F120H5QR@LQFP64 [CX3057-9]  
LM4F121B2QR@LQFP64 [CX3057-9]      LM4F121C4QR@LQFP64 [CX3057-9]  
LM4F121E5QR@LQFP64 [CX3057-9]      LM4F121H5QR@LQFP64 [CX3057-9]  
LM4F130C4QR@LQFP64 [CX3057-9]      LM4F130E5QR@LQFP64 [CX3057-9]  
LM4F130H5QR@LQFP64 [CX3057-9]      LM4F131C4QR@LQFP64 [CX3057-9]  
LM4F131E5QR@LQFP64 [CX3057-9]      LM4F131H5QR@LQFP64 [CX3057-9]  
LM4F210E5QR@LQFP64 [CX3057-9]      LM4F210H5QR@LQFP64 [CX3057-9]  
LM4F211E5QR@LQFP64 [CX3057-9]      LM4F211H5QR@LQFP64 [CX3057-9]  
LM4F230E5QR@LQFP64 [CX3057-9]      LM4F230H5QR@LQFP64 [CX3057-9]  
LM4F231E5QR@LQFP64 [CX3057-9]      LM4F231H5QR@LQFP64 [CX3057-9]  
LSD4FE8231 [CX3011]      LSD4FE8232 [CX3011]  
LSD4FE8233 [CX3011]      MSP430AFE221AIPW [CX1000]  
MSP430AFE221IPW [CX1000]      MSP430AFE222AIPW [CX1000]  
MSP430AFE222IPW [CX1000]      MSP430AFE223AIPW [CX1000]  
MSP430AFE223IPW [CX1000]      MSP430AFE231AIPW [CX1000]  
MSP430AFE231IPW [CX1000]      MSP430AFE232AIPW [CX1000]  
MSP430AFE232IPW [CX1000]      MSP430AFE233AIPW [CX1000]  
MSP430AFE233IPW [CX1000]      MSP430AFE251AIPW [CX1000]  
MSP430AFE251IPW [CX1000]      MSP430AFE252AIPW [CX1000]  
MSP430AFE252IPW [CX1000]  
MSP430AFE253AIPW@TSSOP24 [CX1000]  
MSP430AFE253IPW@TSSOP24 [CX1000]      MSP430F110@SOIC20 [CX1033]  
MSP430F110@TSSOP20 [CX1000]      MSP430F1101@SOIC20 [CX1033]  
MSP430F1101@TSSOP20 [CX1000]      MSP430F1101A@QFN24 [CX4012]  
MSP430F1101A@QFN24 (ISP) [CX0001]      MSP430F1101A@SOIC20 [CX1033]  
MSP430F1101A@SOIC20 (ISP) [CX0001]

MSP430F1101A@TSSOP20 [CX1000]  
MSP430F1101A@TSSOP20(ISP) [CX0001]  
MSP430F1111A@QFN24 [CX4012] MSP430F1111A@QFN24(ISP) [CX0001]  
MSP430F1111A@SOIC20 [CX1033]  
MSP430F1111A@SOIC20(ISP) [CX0001]  
MSP430F1111A@TSSOP20 [CX1000]  
MSP430F1111A@TSSOP20(ISP) [CX0001]  
MSP430F112@SOIC20 [CX1033] MSP430F112@TSSOP20 [CX1000]  
MSP430F1121@SOIC20 [CX1033] MSP430F1121@TSSOP20 [CX1000]  
MSP430F1121A@QFN24 [CX4012] MSP430F1121A@QFN24(ISP) [CX0001]  
MSP430F1121A@SOIC20 [CX1033]  
MSP430F1121A@SOIC20(ISP) [CX0001]  
MSP430F1121A@TSSOP20 [CX1000]  
MSP430F1121A@TSSOP20(ISP) [CX0001]  
MSP430F1122@QFN32 [CX4015] MSP430F1122@SOIC20 [CX1033]  
MSP430F1122@TSSOP20 [CX1000] MSP430F1132@QFN32 [CX4015]  
MSP430F1132@SOIC20 [CX1033] MSP430F1132@TSSOP20 [CX1000]  
MSP430F1222@QFN32 [CX4015] MSP430F1222@SOIC28 [CX1033]  
MSP430F1222@TSSOP28 [CX1001] MSP430F1232@QFN32 [CX4015]  
MSP430F1232@SOIC28 [CX1033] MSP430F1232@TSSOP28 [CX1001]  
MSP430F133@QFN64 [CX4023] MSP430F133@TQFP64 [CX3011]  
MSP430F135@QFN64 [CX4023] MSP430F135@TQFP64 [CX3011]  
MSP430F147@QFN64 [CX4023] MSP430F147@TQFP64 [CX3011]  
MSP430F1471@QFN64 [CX4023] MSP430F1471@TQFP64 [CX3011]  
MSP430F148@QFN64 [CX4023] MSP430F148@TQFP64 [CX3011]  
MSP430F1481@QFN64 [CX4023] MSP430F1481@TQFP64 [CX3011]  
MSP430F149@QFN64 [CX4023] MSP430F149@TQFP64 [CX3011]  
MSP430F1491@QFN64 [CX4023] MSP430F1491@TQFP64 [CX3011]  
MSP430F2001IN [CX0001] MSP430F2001IN(ISP) [CX0001]  
MSP430F2001IN(SPW ISP) [CX0001] MSP430F2001IN(SPW) [CX0001]  
MSP430F2001IPW@TSSOP14 [CX1000]  
MSP430F2001IPW@TSSOP14(ISP) [CX0001]  
MSP430F2001IPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2001IPW@TSSOP14(SPW) [CX1000]  
MSP430F2001IRSA@QFN16 [CX4010]  
MSP430F2001IRSA@QFN16(ISP) [CX0001]  
MSP430F2001IRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2001IRSA@QFN16(SPW) [CX4010]  
MSP430F2001TN [CX0001] MSP430F2001TN(ISP) [CX0001]  
MSP430F2001TN(SPW ISP) [CX0001] MSP430F2001TN(SPW) [CX0001]  
MSP430F2001TPW@TSSOP14 [CX1000]  
MSP430F2001TPW@TSSOP14(ISP) [CX0001]  
MSP430F2001TPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2001TPW@TSSOP14(SPW) [CX1000]  
MSP430F2001TRSA@QFN16 [CX4010]  
MSP430F2001TRSA@QFN16(ISP) [CX0001]  
MSP430F2001TRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2001TRSA@QFN16(SPW) [CX4010]  
MSP430F2002IN [CX0001] MSP430F2002IN(ISP) [CX0001]  
MSP430F2002IN(SPW ISP) [CX0001] MSP430F2002IN(SPW) [CX0001]  
MSP430F2002IPW@TSSOP14 [CX1000]  
MSP430F2002IPW@TSSOP14(ISP) [CX0001]  
MSP430F2002IPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2002IPW@TSSOP14(SPW) [CX1000]  
MSP430F2002IRSA@QFN16 [CX4010]  
MSP430F2002IRSA@QFN16(ISP) [CX0001]  
MSP430F2002IRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2002IRSA@QFN16(SPW) [CX4010]  
MSP430F2002TN [CX0001] MSP430F2002TN(ISP) [CX0001]

MSP430F2002TN(SPW ISP) [CX0001]           MSP430F2002TN(SPW) [CX0001]  
MSP430F2002TPW@TSSOP14 [CX1000]  
MSP430F2002TPW@TSSOP14(ISP) [CX0001]  
MSP430F2002TPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2002TPW@TSSOP14(SPW) [CX1000]  
MSP430F2002TRSA@QFN16 [CX4010]  
MSP430F2002TRSA@QFN16(ISP) [CX0001]  
MSP430F2002TRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2002TRSA@QFN16(SPW) [CX4010]  
MSP430F2003IN [CX0001]                   MSP430F2003IN(ISP) [CX0001]  
MSP430F2003IN(SPW ISP) [CX0001]       MSP430F2003IN(SPW) [CX0001]  
MSP430F2003IPW@TSSOP14 [CX1000]  
MSP430F2003IPW@TSSOP14(ISP) [CX0001]  
MSP430F2003IPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2003IPW@TSSOP14(SPW) [CX1000]  
MSP430F2003IRSA@QFN16 [CX4010]  
MSP430F2003IRSA@QFN16(ISP) [CX0001]  
MSP430F2003IRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2003IRSA@QFN16(SPW) [CX4010]  
MSP430F2003TN [CX0001]                   MSP430F2003TN(ISP) [CX0001]  
MSP430F2003TN(SPW ISP) [CX0001]       MSP430F2003TN(SPW) [CX0001]  
MSP430F2003TPW@TSSOP14 [CX1000]  
MSP430F2003TPW@TSSOP14(ISP) [CX0001]  
MSP430F2003TPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2003TPW@TSSOP14(SPW) [CX1000]  
MSP430F2003TRSA@QFN16 [CX4010]  
MSP430F2003TRSA@QFN16(ISP) [CX0001]  
MSP430F2003TRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2003TRSA@QFN16(SPW) [CX4010]  
MSP430F2011IN [CX0001]                   MSP430F2011IN(ISP) [CX0001]  
MSP430F2011IN(SPW ISP) [CX0001]       MSP430F2011IN(SPW) [CX0001]  
MSP430F2011IPW@TSSOP14 [CX1000]  
MSP430F2011IPW@TSSOP14(ISP) [CX0001]  
MSP430F2011IPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2011IPW@TSSOP14(SPW) [CX1000]  
MSP430F2011IRSA@QFN16 [CX4010]  
MSP430F2011IRSA@QFN16(ISP) [CX0001]  
MSP430F2011IRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2011IRSA@QFN16(SPW) [CX4010]  
MSP430F2011TN [CX0001]                   MSP430F2011TN(ISP) [CX0001]  
MSP430F2011TN(SPW ISP) [CX0001]       MSP430F2011TN(SPW) [CX0001]  
MSP430F2011TPW@TSSOP14 [CX1000]  
MSP430F2011TPW@TSSOP14(ISP) [CX0001]  
MSP430F2011TPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2011TPW@TSSOP14(SPW) [CX1000]  
MSP430F2011TRSA@QFN16 [CX4010]  
MSP430F2011TRSA@QFN16(ISP) [CX0001]  
MSP430F2011TRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2011TRSA@QFN16(SPW) [CX4010]  
MSP430F2012IN [CX0001]                   MSP430F2012IN(ISP) [CX0001]  
MSP430F2012IN(SPW ISP) [CX0001]       MSP430F2012IN(SPW) [CX0001]  
MSP430F2012IPW@TSSOP14 [CX1000]  
MSP430F2012IPW@TSSOP14(ISP) [CX0001]  
MSP430F2012IPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2012IPW@TSSOP14(SPW) [CX1000]  
MSP430F2012IRSA@QFN16 [CX4010]  
MSP430F2012IRSA@QFN16(ISP) [CX0001]  
MSP430F2012IRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2012IRSA@QFN16(SPW) [CX4010]



MSP430F2012TN [CX0001] MSP430F2012TN(ISP) [CX0001]  
MSP430F2012TN(SPW ISP) [CX0001] MSP430F2012TN(SPW) [CX0001]  
MSP430F2012TPW@TSSOP14 [CX1000]  
MSP430F2012TPW@TSSOP14(ISP) [CX0001]  
MSP430F2012TPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2012TPW@TSSOP14(SPW) [CX1000]  
MSP430F2012TRSA@QFN16 [CX4010]  
MSP430F2012TRSA@QFN16(ISP) [CX0001]  
MSP430F2012TRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2012TRSA@QFN16(SPW) [CX4010]  
MSP430F2013IN [CX0001] MSP430F2013IN(ISP) [CX0001]  
MSP430F2013IN(SPW ISP) [CX0001] MSP430F2013IN(SPW) [CX0001]  
MSP430F2013IPW@TSSOP14 [CX1000]  
MSP430F2013IPW@TSSOP14(ISP) [CX0001]  
MSP430F2013IPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2013IPW@TSSOP14(SPW) [CX1000]  
MSP430F2013IRSA@QFN16 [CX4010]  
MSP430F2013IRSA@QFN16(ISP) [CX0001]  
MSP430F2013IRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2013IRSA@QFN16(SPW) [CX4010]  
MSP430F2013TN [CX0001] MSP430F2013TN(ISP) [CX0001]  
MSP430F2013TN(SPW ISP) [CX0001] MSP430F2013TN(SPW) [CX0001]  
MSP430F2013TPW@TSSOP14 [CX1000]  
MSP430F2013TPW@TSSOP14(ISP) [CX0001]  
MSP430F2013TPW@TSSOP14(SPW ISP) [CX0001]  
MSP430F2013TPW@TSSOP14(SPW) [CX1000]  
MSP430F2013TRSA@QFN16 [CX4010]  
MSP430F2013TRSA@QFN16(ISP) [CX0001]  
MSP430F2013TRSA@QFN16(SPW ISP) [CX0001]  
MSP430F2013TRSA@QFN16(SPW) [CX4010]  
MSP430F2101@QFN24(ISP) [CX0001] MSP430F2101@SOIC20(ISP) [CX0001]  
MSP430F2101@TSSOP20(ISP) [CX0001]  
MSP430F2101@TVSOP20(ISP) [CX0001]  
MSP430F2111@QFN24(ISP) [CX0001] MSP430F2111@SOIC20(ISP) [CX0001]  
MSP430F2111@TSSOP20(ISP) [CX0001]  
MSP430F2111@TVSOP20(ISP) [CX0001]  
MSP430F2112AIPW@TSSOP28 [CX1001] MSP430F2112AIRHB@QFN32 [CX4015]  
MSP430F2112ATPW@TSSOP28 [CX1001] MSP430F2112ATRHB@QFN32 [CX4015]  
MSP430F2112IPW@TSSOP28 [CX1001] MSP430F2112IRHB@QFN32 [CX4015]  
MSP430F2112TPW@TSSOP28 [CX1001] MSP430F2112TRHB@QFN32 [CX4015]  
MSP430F2121@QFN24(ISP) [CX0001] MSP430F2121@SOIC20(ISP) [CX0001]  
MSP430F2121@TSSOP20(ISP) [CX0001]  
MSP430F2121@TVSOP20(ISP) [CX0001]  
MSP430F2122AIPW@TSSOP28 [CX1001] MSP430F2122AIRHB@QFN32 [CX4015]  
MSP430F2122ATPW@TSSOP28 [CX1001] MSP430F2122ATRHB@QFN32 [CX4015]  
MSP430F2122IPW@TSSOP28 [CX1001] MSP430F2122IRHB@QFN32 [CX4015]  
MSP430F2122TPW@TSSOP28 [CX1001] MSP430F2122TRHB@QFN32 [CX4015]  
MSP430F2131@QFN24(ISP) [CX0001] MSP430F2131@SOIC20(ISP) [CX0001]  
MSP430F2131@TSSOP20(ISP) [CX0001]  
MSP430F2131@TVSOP20 [CX1023]  
MSP430F2131@TVSOP20(ISP) [CX0001]  
MSP430F2132AIPW@TSSOP28 [CX1001] MSP430F2132AIRHB@QFN32 [CX4015]  
MSP430F2132ATPW@TSSOP28 [CX1001] MSP430F2132ATRHB@QFN32 [CX4015]  
MSP430F2132IPW@TSSOP28 [CX1001] MSP430F2132IRHB@QFN32 [CX4015]  
MSP430F2132TPW@TSSOP28 [CX1001] MSP430F2132TRHB@QFN32 [CX4015]  
MSP430F2232IDA@SSOP38 [CX1027]  
MSP430F2232IDA@SSOP38(ISP) [CX0001]  
MSP430F2232IRHA@QFN40 [CX4017]  
MSP430F2232IRHA@QFN40(ISP) [CX0001]

MSP430F2232IYFF [BBBB] MSP430F2232IYFF(ISP) [BBBB]  
MSP430F2232TDA@SSOP38 [CX1027]  
MSP430F2232TDA@SSOP38(ISP) [CX0001]  
MSP430F2232TRHA@QFN40 [CX4017]  
MSP430F2232TRHA@QFN40(ISP) [CX0001]  
MSP430F2232TYFF [BBBB] MSP430F2232TYFF(ISP) [CX0001]  
MSP430F2234IDA@SSOP38 [CX1027]  
MSP430F2234IDA@SSOP38(ISP) [CX0001]  
MSP430F2234IRHA@QFN40 [CX4017]  
MSP430F2234IRHA@QFN40(ISP) [CX0001]  
MSP430F2234IYFF [BBBB] MSP430F2234IYFF(ISP) [CX0001]  
MSP430F2234TDA@SSOP38 [CX1027]  
MSP430F2234TDA@SSOP38(ISP) [CX0001]  
MSP430F2234TRHA@QFN40 [CX4017]  
MSP430F2234TRHA@QFN40(ISP) [CX0001]  
MSP430F2234TYFF [BBBB] MSP430F2234TYFF(ISP) [CX0001]  
MSP430F2252IDA@SSOP38 [CX1027]  
MSP430F2252IDA@SSOP38(ISP) [CX0001]  
MSP430F2252IRHA@QFN40 [CX4017]  
MSP430F2252IRHA@QFN40(ISP) [CX0001]  
MSP430F2252IYFF [BBBB] MSP430F2252IYFF(ISP) [CX0001]  
MSP430F2252TDA@SSOP38 [CX1027]  
MSP430F2252TDA@SSOP38(ISP) [CX0001]  
MSP430F2252TRHA@QFN40 [CX4017]  
MSP430F2252TRHA@QFN40(ISP) [CX0001]  
MSP430F2252TYFF [BBBB] MSP430F2252TYFF(ISP) [CX0001]  
MSP430F2254IDA@SSOP38 [CX1027]  
MSP430F2254IDA@SSOP38(ISP) [CX0001]  
MSP430F2254IRHA@QFN40 [CX4017]  
MSP430F2254IRHA@QFN40(ISP) [CX0001]  
MSP430F2254IYFF [BBBB] MSP430F2254IYFF(ISP) [CX0001]  
MSP430F2254TDA@SSOP38 [CX1027]  
MSP430F2254TDA@SSOP38(ISP) [CX0001]  
MSP430F2254TRHA@QFN40 [CX4017]  
MSP430F2254TRHA@QFN40(ISP) [CX0001]  
MSP430F2254TYFF [BBBB] MSP430F2254TYFF(ISP) [CX0001]  
MSP430F2272IDA@SSOP38 [CX1027]  
MSP430F2272IDA@SSOP38(ISP) [CX0001]  
MSP430F2272IRHA@QFN40 [CX4017]  
MSP430F2272IRHA@QFN40(ISP) [CX0001]  
MSP430F2272IYFF [BBBB] MSP430F2272IYFF(ISP) [CX0001]  
MSP430F2272TDA@SSOP38 [CX1027]  
MSP430F2272TDA@SSOP38(ISP) [CX0001]  
MSP430F2272TRHA@QFN40 [CX4017]  
MSP430F2272TRHA@QFN40(ISP) [CX0001]  
MSP430F2272TYFF [BBBB] MSP430F2272TYFF(ISP) [CX0001]  
MSP430F2274IDA@SSOP38 [CX1027]  
MSP430F2274IDA@SSOP38(ISP) [CX0001]  
MSP430F2274IRHA@QFN40 [CX4017]  
MSP430F2274IRHA@QFN40(ISP) [CX0001]  
MSP430F2274IYFF [BBBB] MSP430F2274IYFF(ISP) [CX0001]  
MSP430F2274TDA@SSOP38 [CX1027]  
MSP430F2274TDA@SSOP38(ISP) [CX0001]  
MSP430F2274TRHA@QFN40 [CX4017]  
MSP430F2274TRHA@QFN40(ISP) [CX0001]  
MSP430F2274TYFF [BBBB] MSP430F2274TYFF(ISP) [CX0001]  
MSP430F2330IRHA@QFN40(ISP) [CX0001]  
MSP430F2330TRHA@QFN40(ISP) [CX0001]  
MSP430F2350IRHA@QFN40(ISP) [CX0001]

MSP430F2350TRHA@QFN40 (ISP) [CX0001]  
MSP430F2370IRHA@QFN40 (ISP) [CX0001]  
MSP430F2370TRHA@QFN40 (ISP) [CX0001]  
MSP430F412@QFN64 [CX4023]                   MSP430F412@TQFP64 [CX3011]  
MSP430F413@QFN64 [CX4023]                   MSP430F413@TQFP64 [CX3011]  
MSP430F4250@QFN48 [CX4021]                  MSP430F4250@SSOP48 [CX1028]  
MSP430F4260@QFN48 [CX4021]                  MSP430F4260@SSOP48 [CX1028]  
MSP430F4270@QFN48 [CX4021]                  MSP430F4270@SSOP48 [CX1028]  
MSP430F435@TQFP100 [CX3021]                MSP430F435@TQFP80 [CX3016]  
MSP430F4351@TQFP100 [CX3021]              MSP430F4351@TQFP80 [CX3016]  
MSP430F436@TQFP100 [CX3021]                MSP430F436@TQFP80 [CX3016]  
MSP430F4361@TQFP100 [CX3021]              MSP430F4361@TQFP80 [CX3016]  
MSP430F437@TQFP100 [CX3021]                MSP430F437@TQFP80 [CX3016]  
MSP430F4371@TQFP100 [CX3021]              MSP430F4371@TQFP80 [CX3016]  
MSP430F438@TQFP100 [CX3021]                MSP430F438@TQFP80 [CX3016]  
MSP430F4381@TQFP100 [CX3021]              MSP430F4381@TQFP80 [CX3016]  
MSP430F439@TQFP100 [CX3021]                MSP430F439@TQFP80 [CX3016]  
MSP430F4391@TQFP100 [CX3021]              MSP430F4391@TQFP80 [CX3016]  
MSP430F447@TQFP100 [CX3021]                MSP430F4471@TQFP100 [CX3021]  
MSP430F448@TQFP100 [CX3021]                MSP430F4481@TQFP100 [CX3021]  
MSP430F449@TQFP100 [CX3021]                MSP430F4491@TQFP100 [CX3021]  
MSP430F4683IPZ [CX3021]                    MSP430F4684IPZ [CX3021]  
MSP430F4693IPZ [CX3021]                    MSP430F4694IPZ [CX3021]  
MSP430F5131IDA [CX1027]                    MSP430F5131IRSB [CX4039]  
MSP430F5132IDA [CX1027]                    MSP430F5132IRSB [CX4039]  
MSP430F5151IDA [CX1027]                    MSP430F5151IRSB [CX4039]  
MSP430F5152IDA [CX1027]                    MSP430F5152IRSB [CX4039]  
MSP430F5171IDA [CX1027]                    MSP430F5171IRSB [CX4039]  
MSP430F5172IDA [CX1027]                    MSP430F5172IRSB [CX4039]  
MSP430F5304IPT [CX3007]                    MSP430F5304IRGC [CX4023]  
MSP430F5304IRGZ [CX4021]                  MSP430F5304IZQE [CX0001]  
MSP430F5308IPT [CX3007]                    MSP430F5308IRGC [CX4023]  
MSP430F5308IRGZ [CX4021]                  MSP430F5308IZQE [CX0001]  
MSP430F5309IPT [CX3007]                    MSP430F5309IRGC [CX4023]  
MSP430F5309IRGZ [CX4021]                  MSP430F5309IZQE [CX0001]  
MSP430F5310IPT [CX3007]                    MSP430F5310IRGC [CX4023]  
MSP430F5310IRGZ [CX4021]                  MSP430F5310IZQE [CX0001]  
MSP430F5324IRGC [CX4023]                  MSP430F5325IPN [CX3016]  
MSP430F5325IZQE [CX0001]                  MSP430F5326IRGC [CX4023]  
MSP430F5327IPN [CX3016]                    MSP430F5327IZQE [CX0001]  
MSP430F5328IRGC [CX4023]                  MSP430F5329IPN [CX3016]  
MSP430F5329IZQE [CX0001]                  MSP430F5333AIPZ [CX3021]  
MSP430F5333AIZQW [CX5150]                MSP430F5333IPZ [CX3021]  
MSP430F5333IZQW [CX5150]                MSP430F5334AIPZ [CX3021]  
MSP430F5334AIZQW [CX5150]                MSP430F5334IPZ [CX3021]  
MSP430F5334IZQW [CX5150]                MSP430F5335AIPZ [CX3021]  
MSP430F5335AIZQW [CX5150]                MSP430F5335IPZ [CX3021]  
MSP430F5335IZQW [CX5150]                MSP430F5336AIPZ [CX3021]  
MSP430F5336AIZQW [CX5150]                MSP430F5336IPZ [CX3021]  
MSP430F5336IZQW [CX5150]                MSP430F5338AIPZ [CX3021]  
MSP430F5338AIZQW [CX5150]                MSP430F5338IPZ [CX3021]  
MSP430F5338IZQW [CX5150]                MSP430F5340IRGZ [CX4021]  
MSP430F5341IRGZ [CX4021]                MSP430F5342IRGZ [CX4021]  
MSP430F5418@QFP80 [CX3016]                MSP430F5418A@QFP80 [CX3016]  
MSP430F5419@QFP100 [CX3021]              MSP430F5419A@QFP100 [CX3021]  
MSP430F5435@QFP80 [CX3016]                MSP430F5435A@QFP80 [CX3016]  
MSP430F5436@QFP100 [CX3021]              MSP430F5436A@QFP100 [CX3021]  
MSP430F5437@QFP80 [CX3016]                MSP430F5437A@QFP80 [CX3016]  
MSP430F5438@QFP100 [CX3021]              MSP430F5438A@QFP100 [CX3021]

MSP430F5500@BGA80 [CX0001]      MSP430F5500@QFN48 [CX4021]  
MSP430F5500@QFN64 [CX4023]      MSP430F5500@QFP48 [CX3007]  
MSP430F5500IPT [CX3007]          MSP430F5500IRGC [CX4023]  
MSP430F5500IRGZ [CX4021]        MSP430F5500IZQE [CX0001]  
MSP430F5501@BGA80 [CX0001]      MSP430F5501@QFN48 [CX4021]  
MSP430F5501@QFN64 [CX4023]      MSP430F5501@QFP48 [CX3007]  
MSP430F5501IPT [CX3007]          MSP430F5501IRGC [CX4023]  
MSP430F5501IRGZ [CX4021]        MSP430F5501IZQE [CX0001]  
MSP430F5502@BGA80 [CX0001]      MSP430F5502@QFN48 [CX4021]  
MSP430F5502@QFN64 [CX4023]      MSP430F5502@QFP48 [CX3007]  
MSP430F5502IPT [CX3007]          MSP430F5502IRGC [CX4023]  
MSP430F5502IRGZ [CX4021]        MSP430F5502IZQE [CX0001]  
MSP430F5503@BGA80 [CX0001]      MSP430F5503@QFN48 [CX4021]  
MSP430F5503@QFN64 [CX4023]      MSP430F5503@QFP48 [CX3007]  
MSP430F5503IPT [CX3007]          MSP430F5503IRGC [CX4023]  
MSP430F5503IRGZ [CX4021]        MSP430F5503IZQE [CX0001]  
MSP430F5504@BGA80 [CX0001]      MSP430F5504@QFN48 [CX4021]  
MSP430F5504@QFN64 [CX4023]      MSP430F5504@QFP48 [CX3007]  
MSP430F5504IPT [CX3007]          MSP430F5504IRGC [CX4023]  
MSP430F5504IRGZ [CX4021]        MSP430F5504IZQE [CX0001]  
MSP430F5505@BGA80 [CX0001]      MSP430F5505@QFN48 [CX4021]  
MSP430F5505@QFN64 [CX4023]      MSP430F5505@QFP48 [CX3007]  
MSP430F5505IPT [CX3007]          MSP430F5505IRGC [CX4023]  
MSP430F5505IRGZ [CX4021]        MSP430F5505IZQE [CX0001]  
MSP430F5506@BGA80 [CX0001]      MSP430F5506@QFN48 [CX4021]  
MSP430F5506@QFN64 [CX4023]      MSP430F5506@QFP48 [CX3007]  
MSP430F5506IPT [CX3007]          MSP430F5506IRGC [CX4023]  
MSP430F5506IRGZ [CX4021]        MSP430F5506IZQE [CX0001]  
MSP430F5507@BGA80 [CX0001]      MSP430F5507@QFN48 [CX4021]  
MSP430F5507@QFN64 [CX4023]      MSP430F5507@QFP48 [CX3007]  
MSP430F5507IPT [CX3007]          MSP430F5507IRGC [CX4023]  
MSP430F5507IRGZ [CX4021]        MSP430F5507IZQE [CX0001]  
MSP430F5508@BGA80 [CX0001]      MSP430F5508@QFN48 [CX4021]  
MSP430F5508@QFN64 [CX4023]      MSP430F5508@QFP48 [CX3007]  
MSP430F5508IPT [CX3007]          MSP430F5508IRGC [CX4023]  
MSP430F5508IRGZ [CX4021]        MSP430F5508IZQE [CX0001]  
MSP430F5509@BGA80 [CX0001]      MSP430F5509@QFN48 [CX4021]  
MSP430F5509@QFN64 [CX4023]      MSP430F5509@QFP48 [CX3007]  
MSP430F5509IPT [CX3007]          MSP430F5509IRGC [CX4023]  
MSP430F5509IRGZ [CX4021]        MSP430F5509IZQE [CX0001]  
MSP430F5510@BGA80 [CX0001]      MSP430F5510@QFN48 [CX4021]  
MSP430F5510@QFN64 [CX4023]      MSP430F5510@QFP48 [CX3007]  
MSP430F5510IPT [CX3007]          MSP430F5510IRGC [CX4023]  
MSP430F5510IRGZ [CX4021]        MSP430F5510IZQE [CX0001]  
MSP430F5511@QFP80 [CX3016]        MSP430F5513@QFN64 [CX4023]  
MSP430F5514@QFN64 [CX4023]        MSP430F5515@QFP80 [CX3016]  
MSP430F5517@QFP80 [CX3016]        MSP430F5519@QFP80 [CX3016]  
MSP430F5521@QFP80 [CX3016]        MSP430F5522@QFN64 [CX4023]  
MSP430F5524@QFN64 [CX4023]        MSP430F5525@QFP80 [CX3016]  
MSP430F5526@QFN64 [CX4023]        MSP430F5527@QFP80 [CX3016]  
MSP430F5528@QFN64 [CX4023]        MSP430F5529@QFP80 [CX3016]  
MSP430F6433AIPZ [CX3021]          MSP430F6433AIZQW [CX5150]  
MSP430F6433IPZ [CX3021]          MSP430F6433IZQW [CX5150]  
MSP430F6434AIPZ [CX3021]          MSP430F6434AIZQW [CX5150]  
MSP430F6434IPZ [CX3021]          MSP430F6434IZQW [CX5150]  
MSP430F6435AIPZ [CX3021]          MSP430F6435AIZQW [CX5150]  
MSP430F6435IPZ [CX3021]          MSP430F6435IZQW [CX5150]  
MSP430F6436AIPZ [CX3021]          MSP430F6436AIZQW [CX5150]  
MSP430F6436IPZ [CX3021]          MSP430F6436IZQW [CX5150]

MSP430F6438AIPZ [CX3021]                   MSP430F6438AIZQW [CX5150]  
MSP430F6438IPZ [CX3021]                   MSP430F6438IZQW [CX5150]  
MSP430F6720IPN [CX3016]                   MSP430F6720IPZ [CX3021]  
MSP430F6721IPN [CX3016]                   MSP430F6721IPZ [CX3021]  
MSP430F6723IPN [CX3016]                   MSP430F6723IPZ [CX3021]  
MSP430F6724IPN [CX3016]                   MSP430F6724IPZ [CX3021]  
MSP430F6725IPN [CX3016]                   MSP430F6725IPZ [CX3021]  
MSP430F6726IPN [CX3016]                   MSP430F6726IPZ [CX3021]  
MSP430F6730IPN [CX3016]                   MSP430F6730IPZ [CX3021]  
MSP430F6731IPN [CX3016]                   MSP430F6731IPZ [CX3021]  
MSP430F6733IPN [CX3016]                   MSP430F6733IPZ [CX3021]  
MSP430F6734IPN [CX3016]                   MSP430F6734IPZ [CX3021]  
MSP430F6735IPN [CX3016]                   MSP430F6735IPZ [CX3021]  
MSP430F6736IPN [CX3016]                   MSP430F6736IPZ [CX3021]  
MSP430FG4250@QFN48 [CX4021]               MSP430FG4250@SSOP48 [CX1028]  
MSP430FG4260@QFN48 [CX4021]               MSP430FG4260@SSOP48 [CX1028]  
MSP430FG4270@QFN48 [CX4021]               MSP430FG4270@SSOP48 [CX1028]  
MSP430FR5720IPW [CX1001]                   MSP430FR5720IRGE [CX4012]  
MSP430FR5721IDA [CX1027]                   MSP430FR5721IRHA [CX4017]  
MSP430FR5722IPW [CX1001]                   MSP430FR5722IRGE [CX4012]  
MSP430FR5723IDA [CX1027]                   MSP430FR5723IRHA [CX4017]  
MSP430FR5724IPW [CX1001]                   MSP430FR5724IRGE [CX4012]  
MSP430FR5725IDA [CX1027]                   MSP430FR5725IRHA [CX4017]  
MSP430FR5726IPW [CX1001]                   MSP430FR5726IRGE [CX4012]  
MSP430FR5727IDA [CX1027]                   MSP430FR5727IRHA [CX4017]  
MSP430FR5728IPW [CX1001]                   MSP430FR5728IRGE [CX4012]  
MSP430FR5729IDA [CX1027]                   MSP430FR5729IRHA [CX4017]  
MSP430FR5730IPW [CX1001]                   MSP430FR5730IRGE [CX4012]  
MSP430FR5731IDA [CX1027]                   MSP430FR5731IRHA [CX4017]  
MSP430FR5732IPW [CX1001]                   MSP430FR5732IRGE [CX4012]  
MSP430FR5733IDA [CX1027]                   MSP430FR5733IRHA [CX4017]  
MSP430FR5734IPW [CX1001]                   MSP430FR5734IRGE [CX4012]  
MSP430FR5735IDA [CX1027]                   MSP430FR5735IRHA [CX4017]  
MSP430FR5736IPW [CX1001]                   MSP430FR5736IRGE [CX4012]  
MSP430FR5737IDA [CX1027]                   MSP430FR5737IRHA [CX4017]  
MSP430FR5738IPW [CX1001]                   MSP430FR5738IRGE [CX4012]  
MSP430FR5739IDA [CX1027]                   MSP430FR5739IRHA [CX4017]  
MSP430FR5969IRGZ [CX4021]                   MSP430G2001IN [CX0001]  
MSP430G2001IPW@TSSOP14 [CX1000]           MSP430G2001IRSA@QFN16 [CX4010]  
MSP430G2001TN [CX0001]                   MSP430G2001TPW@TSSOP14 [CX1000]  
MSP430G2001TRSA@QFN16 [CX4010]           MSP430G2002IN [CX0001]  
MSP430G2002IPW14@TSSOP14 [CX1000]       MSP430G2011IN [CX0001]  
MSP430G2002IPW20@TSSOP20 [CX1001]       MSP430G2011IRSA@QFN16 [CX4010]  
MSP430G2002IRSA@QFN16 [CX4010]           MSP430G2011TPW@TSSOP14 [CX1000]  
MSP430G2011IPW@TSSOP14 [CX1000]       MSP430G2012IN [CX0001]  
MSP430G2011TN [CX0001]                   MSP430G2012IPW20 [CX1001]  
MSP430G2011TRSA@QFN16 [CX4010]           MSP430G2013IN20 [CX0001]  
MSP430G2012IPW14 [CX1000]               MSP430G2013IPW28 [CX1001]  
MSP430G2012IRSA [CX4010]               MSP430G2021IN [CX0001]  
MSP430G2013IPW20 [CX1001]               MSP430G2021IRSA@QFN16 [CX4010]  
MSP430G2013IRH32 [CX4015]               MSP430G2021TPW@TSSOP14 [CX1000]  
MSP430G2021IPW@TSSOP14 [CX1000]       MSP430G2031IN [CX0001]  
MSP430G2021TN [CX0001]                   MSP430G2031IRSA@QFN16 [CX4010]  
MSP430G2021TRSA@QFN16 [CX4010]           MSP430G2031TPW@TSSOP14 [CX1000]  
MSP430G2031IPW@TSSOP14 [CX1000]       MSP430G2032IN [CX0001]  
MSP430G2031TN [CX0001]                   MSP430G2032IPW14@TSSOP14 [CX1000]  
MSP430G2031TRSA@QFN16 [CX4010]           MSP430G2032IPW20@TSSOP20 [CX1001]  
MSP430G2032IPW14@TSSOP14 [CX1000]  
MSP430G2032IPW20@TSSOP20 [CX1001]

MSP430G2032IRSA@QFN16 [CX4010]  
MSP430G2052IPW14 [CX1000]  
MSP430G2052IRSA [CX4010]  
MSP430G2053IPW20 [CX1001]  
MSP430G2053IRH32 [CX4015]  
MSP430G2101IPW@TSSOP14 [CX1000]  
MSP430G2101TN [CX0001]  
MSP430G2101TRSA@QFN16 [CX4010]  
MSP430G2102IPW14@TSSOP14 [CX1000]  
MSP430G2102IPW20@TSSOP20 [CX1001]  
MSP430G2102IRSA@QFN16 [CX4010]  
MSP430G2111IPW@TSSOP14 [CX1000]  
MSP430G2111TN [CX0001]  
MSP430G2111TRSA@QFN16 [CX4010]  
MSP430G2112IPW14 [CX1000]  
MSP430G2112IRSA [CX4010]  
MSP430G2113IPW20 [CX1001]  
MSP430G2113IRH32 [CX4015]  
MSP430G2121IPW@TSSOP14 [CX1000]  
MSP430G2121TN [CX0001]  
MSP430G2121TRSA@QFN16 [CX4010]  
MSP430G2131IPW@TSSOP14 [CX1000]  
MSP430G2131TN [CX0001]  
MSP430G2131TRSA@QFN16 [CX4010]  
MSP430G2132IPW14@TSSOP14 [CX1000]  
MSP430G2132IPW20@TSSOP20 [CX1001]  
MSP430G2132IRSA@QFN16 [CX4010]  
MSP430G2152IPW14 [CX1000]  
MSP430G2152IRSA [CX4010]  
MSP430G2153IPW20 [CX1001]  
MSP430G2153IRH32 [CX4015]  
MSP430G2201IPW@TSSOP14 [CX1000]  
MSP430G2201TN [CX0001]  
MSP430G2201TRSA@QFN16 [CX4010]  
MSP430G2202IPW14@TSSOP14 [CX1000]  
MSP430G2202IPW20@TSSOP20 [CX1001]  
MSP430G2202IRSA@QFN16 [CX4010]  
MSP430G2203IPW20 [CX1001]  
MSP430G2203IRH32 [CX4015]  
MSP430G2210IDR [CX1016]  
MSP430G2211IPW@TSSOP14 [CX1000]  
MSP430G2211TN [CX0001]  
MSP430G2211TRSA@QFN16 [CX4010]  
MSP430G2212IPW14 [CX1000]  
MSP430G2212IRSA [CX4010]  
MSP430G2213IPW20 [CX1001]  
MSP430G2213IRH32 [CX4015]  
MSP430G2221IPW@TSSOP14 [CX1000]  
MSP430G2221TN [CX0001]  
MSP430G2221TRSA@QFN16 [CX4010]  
MSP430G2230IDR [CX1016]  
MSP430G2231IPW@TSSOP14 [CX1000]  
MSP430G2231TN [CX0001]  
MSP430G2231TRSA@QFN16 [CX4010]  
MSP430G2232IPW14@TSSOP14 [CX1000]  
MSP430G2232IPW20@TSSOP20 [CX1001]  
MSP430G2232IRSA@QFN16 [CX4010]  
MSP430G2233IPW20 [CX1001]  
MSP430G2233IRH32 [CX4015]

MSP430G2052IN [CX0001]  
MSP430G2052IPW20 [CX1001]  
MSP430G2053IN20 [CX0001]  
MSP430G2053IPW28 [CX1001]  
MSP430G2101IN [CX0001]  
MSP430G2101IRSA@QFN16 [CX4010]  
MSP430G2101TPW@TSSOP14 [CX1000]  
MSP430G2102IN [CX0001]  
MSP430G2111IN [CX0001]  
MSP430G2111IRSA@QFN16 [CX4010]  
MSP430G2111TPW@TSSOP14 [CX1000]  
MSP430G2112IN [CX0001]  
MSP430G2112IPW20 [CX1001]  
MSP430G2113IN20 [CX0001]  
MSP430G2113IPW28 [CX1001]  
MSP430G2121IN [CX0001]  
MSP430G2121IRSA@QFN16 [CX4010]  
MSP430G2121TPW@TSSOP14 [CX1000]  
MSP430G2131IN [CX0001]  
MSP430G2131IRSA@QFN16 [CX4010]  
MSP430G2131TPW@TSSOP14 [CX1000]  
MSP430G2132IN [CX0001]  
MSP430G2152IN [CX0001]  
MSP430G2152IPW20 [CX1001]  
MSP430G2153IN20 [CX0001]  
MSP430G2153IPW28 [CX1001]  
MSP430G2201IN [CX0001]  
MSP430G2201IRSA@QFN16 [CX4010]  
MSP430G2201TPW@TSSOP14 [CX1000]  
MSP430G2202IN [CX0001]  
MSP430G2203IN20 [CX0001]  
MSP430G2203IPW28 [CX1001]  
MSP430G2210ID [CX1016]  
MSP430G2211IN [CX0001]  
MSP430G2211IRSA@QFN16 [CX4010]  
MSP430G2211TPW@TSSOP14 [CX1000]  
MSP430G2212IN [CX0001]  
MSP430G2212IPW20 [CX1001]  
MSP430G2213IN20 [CX0001]  
MSP430G2213IPW28 [CX1001]  
MSP430G2221IN [CX0001]  
MSP430G2221IRSA@QFN16 [CX4010]  
MSP430G2221TPW@TSSOP14 [CX1000]  
MSP430G2230ID [CX1016]  
MSP430G2231IN [CX0001]  
MSP430G2231IRSA@QFN16 [CX4010]  
MSP430G2231TPW@TSSOP14 [CX1000]  
MSP430G2232IN [CX0001]  
MSP430G2233IN20 [CX0001]  
MSP430G2233IPW28 [CX1001]  
MSP430G2252IN [CX0001]

MSP430G2252IPW14 [CX1000]  
MSP430G2252IRSA [CX4010]  
MSP430G2253IPW20 [CX1001]  
MSP430G2253IRH32 [CX4015]  
MSP430G2302IN [CX0001]  
MSP430G2302IPW14@TSSOP14 [CX1000]  
MSP430G2302IPW20@TSSOP20 [CX1001]  
MSP430G2302IRSA@QFN16 [CX4010]  
MSP430G2303IPW20 [CX1001]  
MSP430G2303IRH32 [CX4015]  
MSP430G2312IPW14 [CX1000]  
MSP430G2312IRSA [CX4010]  
MSP430G2313IPW20 [CX1001]  
MSP430G2313IRH32 [CX4015]  
MSP430G2332IPW14@TSSOP14 [CX1000]  
MSP430G2332IPW20@TSSOP20 [CX1001]  
MSP430G2332IRSA@QFN16 [CX4010]  
MSP430G2333IPW20 [CX1001]  
MSP430G2333IRH32 [CX4015]  
MSP430G2352IPW14 [CX1000]  
MSP430G2352IRSA [CX4010]  
MSP430G2353IPW20 [CX1001]  
MSP430G2353IRH32 [CX4015]  
MSP430G2402IPW14@TSSOP14 [CX1000]  
MSP430G2402IPW20@TSSOP20 [CX1001]  
MSP430G2402IRSA@QFN16 [CX4010]  
MSP430G2403IPW20 [CX1001]  
MSP430G2403IRH32 [CX4015]  
MSP430G2412IPW14 [CX1000]  
MSP430G2412IRSA [CX4010]  
MSP430G2413IPW20 [CX1001]  
MSP430G2413IRH32 [CX4015]  
MSP430G2432IPW14@TSSOP14 [CX1000]  
MSP430G2432IPW20@TSSOP20 [CX1001]  
MSP430G2432IRSA@QFN16 [CX4010]  
MSP430G2433IPW20 [CX1000]  
MSP430G2433IRH32 [CX4015]  
MSP430G2452IPW14 [CX1000]  
MSP430G2452IRSA [CX4010]  
MSP430G2453IPW20 [CX1000]  
MSP430G2453IRH32 [CX4015]  
MSP430G2503IPW20 [CX1001]  
MSP430G2503IRH32 [CX4015]  
MSP430G2513IPW20 [CX1001]  
MSP430G2513IRH32 [CX4015]  
MSP430G2533IPW20 [CX1000]  
MSP430G2533IRH32 [CX4015]  
MSP430G2553IPW20 [CX1000]  
MSP430G2553IRH32 [CX4015]  
MSP430V103@QFP64 [CX3011]  
TMS320F28020@TSSOP38 [CX1027]  
TMS320F28021@TSSOP38 [CX1027]  
TMS320F28022@TSSOP38 [CX1027]  
TMS320F28023@TSSOP38 [CX1027]  
TMS320F28030@LQFP80 [CX3016]  
TMS320F28031@LQFP80 [CX3016]  
TMS320F28032@LQFP80 [CX3016]  
TMS320F28033@LQFP80 [CX3016]  
TMS320F28034@LQFP80 [CX3016]  
TMS320F28035@LQFP80 [CX3016]  
MSP430G2252IPW20 [CX1001]  
MSP430G2253IN20 [CX0001]  
MSP430G2253IPW28 [CX1001]  
MSP430G2253IRHS [CX4030]  
MSP430G2303IN20 [CX0001]  
MSP430G2303IPW28 [CX1001]  
MSP430G2312IN [CX0001]  
MSP430G2312IPW20 [CX1001]  
MSP430G2313IN20 [CX0001]  
MSP430G2313IPW28 [CX1001]  
MSP430G2332IN [CX0001]  
MSP430G2333IN20 [CX0001]  
MSP430G2333IPW28 [CX1001]  
MSP430G2352IN [CX0001]  
MSP430G2352IPW20 [CX1001]  
MSP430G2353IN20 [CX0001]  
MSP430G2353IPW28 [CX1001]  
MSP430G2402IN [CX0001]  
MSP430G2403IN20 [CX0001]  
MSP430G2403IPW28 [CX1001]  
MSP430G2412IN [CX0001]  
MSP430G2412IPW20 [CX1001]  
MSP430G2413IN20 [CX0001]  
MSP430G2413IPW28 [CX1001]  
MSP430G2432IN [CX0001]  
MSP430G2433IN20 [CX0001]  
MSP430G2433IPW28 [CX1001]  
MSP430G2452IN [CX0001]  
MSP430G2452IPW20 [CX1000]  
MSP430G2453IN20 [CX0001]  
MSP430G2453IPW28 [CX1001]  
MSP430G2503IN20 [CX0001]  
MSP430G2503IPW28 [CX1001]  
MSP430G2513IN20 [CX0001]  
MSP430G2513IPW28 [CX1001]  
MSP430G2533IN20 [CX0001]  
MSP430G2533IPW28 [CX1001]  
MSP430G2553IN20 [CX0001]  
MSP430G2553IPW28 [CX1001]  
MSP430V103@QFN64 [CX4023]  
TMS320F28020@LQFP48 [CX3007]  
TMS320F28021@LQFP48 [CX3007]  
TMS320F28022@LQFP48 [CX3007]  
TMS320F28023@LQFP48 [CX3007]  
TMS320F28030@LQFP64 [CX3011]  
TMS320F28031@LQFP64 [CX3011]  
TMS320F28032@LQFP64 [CX3011]  
TMS320F28033@LQFP64 [CX3011]  
TMS320F28034@LQFP64 [CX3011]  
TMS320F28035@LQFP64 [CX3011]

TMS320F28035@LQFP80 [CX3016]	TMS320F2806@BGA100 [CX5106]
TMS320F2806@LQFP100 [CX3043]	TMS37122 [CX1000]
TMS37122A [CX1000]	TPS65168@QFN40 [CX4039]
TPS65177@QFN40 [CX4017]	
TPS65177@QFN40(left down) [CX4017]	
TPS65178@QFN48 [CX4043]	TPS65835RKPR@QFN40 [CX4039]
TPS65836RKPR@QFN40 [CX4039]	XMS430FR5720IPW [CX1001]
XMS430FR5720IRGE [CX4012]	XMS430FR5721IDA [CX1027]
XMS430FR5721IRHA [CX4017]	XMS430FR5722IPW [CX1001]
XMS430FR5722IRGE [CX4012]	XMS430FR5723IDA [CX1027]
XMS430FR5723IRHA [CX4017]	XMS430FR5724IPW [CX1001]
XMS430FR5724IRGE [CX4012]	XMS430FR5725IDA [CX1027]
XMS430FR5725IRHA [CX4017]	XMS430FR5726IPW [CX1001]
XMS430FR5726IRGE [CX4012]	XMS430FR5727IDA [CX1027]
XMS430FR5727IRHA [CX4017]	XMS430FR5728IPW [CX1001]
XMS430FR5728IRGE [CX4012]	XMS430FR5729IDA [CX1027]
XMS430FR5729IRHA [CX4017]	XMS430FR5730IPW [CX1001]
XMS430FR5730IRGE [CX4012]	XMS430FR5731IDA [CX1027]
XMS430FR5731IRHA [CX4017]	XMS430FR5732IPW [CX1001]
XMS430FR5732IRGE [CX4012]	XMS430FR5733IDA [CX1027]
XMS430FR5733IRHA [CX4017]	XMS430FR5734IPW [CX1001]
XMS430FR5734IRGE [CX4012]	XMS430FR5735IDA [CX1027]
XMS430FR5735IRHA [CX4017]	XMS430FR5736IPW [CX1001]
XMS430FR5736IRGE [CX4012]	XMS430FR5737IDA [CX1027]
XMS430FR5737IRHA [CX4017]	XMS430FR5738IPW [CX1001]
XMS430FR5738IRGE [CX4012]	XMS430FR5739IDA [CX1027]
XMS430FR5739IRHA [CX4017]	XMS430FR5969IRGZ [CX4021]

## TI-CUSTOMER

### MICROCONTROLLER

LM3S1911@BGA108(bosen) [CX5107]	LM3S1911@TQFP100 [CX3021]
LM3S1911@TQFP100(TONGCHI) [CX3021]	

## TMC

### E (E) PROM/FRAM/NVRAM

24A01 [CX0001]	24A01@SOIC8 [CX1045]
24A01@TSSOP8 [CX1059]	24A02 [CX0001]
24A02@SOIC8 [CX1045]	24A02@TSSOP8 [CX1059]
24A04 [CX0001]	24A04@SOIC8 [CX1045]
24A04@TSSOP8 [CX1059]	24A08 [CX0001]
24A08@SOIC8 [CX1045]	24A08@TSSOP8 [CX1059]
24A16 [CX0001]	24A16@SOIC8 [CX1045]
24A16@TSSOP8 [CX1059]	93LC46(08bit) [CX0001]
93LC46(08bit)@SOIC8 [CX1045]	93LC46(08bit)@TSSOP8 [CX1059]
93LC46(16bit) [CX0001]	93LC46(16bit)@SOIC8 [CX1045]
93LC46(16bit)@TSSOP8 [CX1059]	93LC56(08bit) [CX0001]
93LC56(08bit)@SOIC8 [CX1045]	93LC56(08bit)@TSSOP8 [CX1059]
93LC56(16bit) [CX0001]	93LC56(16bit)@SOIC8 [CX1045]
93LC56(16bit)@TSSOP8 [CX1059]	93LC57 [CX0001]
93LC57@SOIC8 [CX1045]	93LC57@TSSOP8 [CX1059]
93LC66(08bit) [CX0001]	93LC66(08bit)@SOIC8 [CX1045]
93LC66(08bit)@TSSOP8 [CX1059]	93LC66(16bit) [CX0001]
93LC66(16bit)@SOIC8 [CX1045]	93LC66(16bit)@TSSOP8 [CX1059]



93LC86(08bit) [CX0001]  
93LC86(08bit)@TSSOP8 [CX1059]  
93LC86(16bit)@SOIC8 [CX1045]

93LC86(08bit)@SOIC8 [CX1045]  
93LC86(16bit) [CX0001]  
93LC86(16bit)@TSSOP8 [CX1059]

## TOSHIBA

### E (E) PROM/FRAM/NVRAM

TC541000AF@PLCC32 [CX0001]  
TC541001AF@PLCC32 [CX0001]  
TC54256AF [CX0001]  
TC54256AP [CX0001]  
TC544000P [CX0001]  
TC54512AP [CX0001]  
TC571000AD [CX0001]  
TC571001AD [CX0001]  
TC571024D [CX0001]  
TC57256A [CX0001]  
TC57256ADI [CX0001]  
TC574000D [CX0001]  
TC574200D [CX0001]  
TC57512AD [CX0001]  
TC57H1000AD [CX0001]  
TC57H256D [CX0001]  
TC58256AFT@TSOP48 [CX1004]  
TC58BVG0S3HTA00@TSOP48 [CX1004-1]  
TC58BVG1S3HTA00@TSOP48 [CX1004-1]  
TC58DVG02A1FT00@TSOP48 [CX1004]  
TC58DVG02D5TA00@TSOP48 [CX1004-1]  
TC58DVG3S0ETA00@TSOP48 [CX1004-1]  
TC58DVM72A1FT00@TSOP48 [CX1004]  
TC58DVM82A1FT00@TSOP48 [CX1004]  
TC58DVM92A5TA00@TSOP48 [CX1004]  
TC58F400@TSOP48 [CX1004]  
TC58F401@TSOP48 [CX1004]  
TC58FVB008FT@TSOP40 [CX1006]  
TC58FVB160AFT@TSOP48 [CX1004]  
TC58FVB160FT@TSOP48 [CX1004]  
TC58FVB321XB@TFBGA56 [CX5046]  
TC58FVB400FT@TSOP48 [CX1004]  
TC58FVB641XB@TFBGA63 [CX5046]  
TC58FVB800FT@TSOP48 [CX1004]  
TC58FVM5B2ATG@TSOP48 [CX1004]  
TC58FVM5B2AXG@TFBGA56 [CX5005]  
TC58FVM5B3ATG@TSOP48 [CX1004]  
TC58FVM5B3AXG@TFBGA56 [CX5005]  
TC58FVM5T2ATG@TSOP48 [CX1004]  
TC58FVM5T2AXG@TFBGA56 [CX5005]  
TC58FVM5T3ATG@TSOP48 [CX1004]  
TC58FVM5T3AXG@TFBGA56 [CX5005]  
TC58FVM6B2AXB@TFBGA63 [CX5005]  
TC58FVM6B5BXG@TFBGA56 [CX5005]  
TC58FVM6T2AXB@TFBGA63 [CX5005]  
TC58FVM6T5BXG@TFBGA56 [CX5005]  
TC58FVM7B2AT@TSOP56 [CX1011]  
TC58FVM7B5BXG@FBGA80 [CX5005]  
TC58FVM7T5BTG@TSOP56 [CX1055]  
TC58FVT004FT@TSOP40 [CX1006]

TC541000AP [CX0001]  
TC541001AP [CX0001]  
TC54256AF@SOIC28  
TC54256AP@SOIC28  
TC54512AF [CX0001]  
TC571000 [CX0001]  
TC571000D [CX0001]  
TC571001D [CX0001]  
TC57256 [CX0001]  
TC57256AD [CX0001]  
TC57256D [CX0001]  
TC574096D [CX0001]  
TC57512 [CX0001]  
TC578200D [CX0001]  
TC57H1001AD [CX0001]  
TC58128AFT@TSOP48 [CX1004]  
TC58512FT@TSOP48 [CX1004]  
TC58DVM72A1TG00@TSOP48 [CX1004]  
TC58DVM92A1FT00@TSOP48 [CX1004]  
TC58F400@PSOP44 [CX1014]  
TC58F401@PSOP44 [CX1014]  
TC58FVB004FT@TSOP40 [CX1006]  
TC58FVB016FT@TSOP40 [CX1006]  
TC58FVB160AXB@TFBGA48 [CX5002]  
TC58FVB321FT@TSOP48 [CX1004]  
TC58FVB400F@PSOP44 [CX1014]  
TC58FVB641FT@TSOP48 [CX1004]  
TC58FVB800F@PSOP44 [CX1014]  
TC58FVM5B2AFT@TSOP48 [CX1004]  
TC58FVM5B2AXB@TFBGA56 [CX5005]  
TC58FVM5B3AFT@TSOP48 [CX1004]  
TC58FVM5B3AXB@TFBGA56 [CX5005]  
TC58FVM5T2AFT@TSOP48 [CX1004]  
TC58FVM5T2AXB@TFBGA56 [CX5005]  
TC58FVM5T3AFT@TSOP48 [CX1004]  
TC58FVM5T3AXB@TFBGA56 [CX5005]  
TC58FVM6B2AFT@TSOP48 [CX1004]  
TC58FVM6B5BTG@TSOP48 [CX1004]  
TC58FVM6T2AFT@TSOP48 [CX1004]  
TC58FVM6T5BTG@TSOP48 [CX1004]  
TC58FVM7B2AFT@TSOP56 [CX1055]  
TC58FVM7B5BTG@TSOP56 [CX1055]  
TC58FVM7T2AFT@TSOP56 [CX1055]  
TC58FVM7T5BXG@FBGA80 [CX5005]  
TC58FVT008FT@TSOP40 [CX1006]

TC58FVT016FT@TSOP40 [CX1006]	TC58FVT160AFT@TSOP48 [CX1004]
TC58FVT160AXB@TFBGA48 [CX5002]	TC58FVT160FT@TSOP48 [CX1004]
TC58FVT321FT@TSOP48 [CX1004]	TC58FVT321XB@TFBGA56 [CX5046]
TC58FVT400F@PSOP44 [CX1014]	TC58FVT400FT@TSOP48 [CX1004]
TC58FVT641FT@TSOP48 [CX1004]	TC58FVT641XB@TFBGA63 [CX5046]
TC58FVT800F@PSOP44 [CX1014]	TC58FVT800FT@TSOP48 [CX1004]
TC58FYB160FT@TSOP48 [CX1004]	TC58FYT160FT@TSOP48 [CX1004]
TC58NVG0ABEBAI4@BGA63 [CX5005]	TC58NVG0S3AFT05@TSOP48 [CX1004]
TC58NVG0S3CTA00@TSOP48 [CX1004]	
TC58NVG0S3ETA00@TSOP48 [CX1004-1]	
TC58NVG0S3ETAI0@TSOP48 [CX1004-1]	
TC58NVG0S3ETAIB@TSOP48 [CX1004-1]	
TC58NVG0S3HTA00@TSOP48 [CX1004-1]	
TC58NVG1S3ETA00@TSOP48 [CX1004-3]	
TC58NVG1S3ETAI0@TSOP48 [CX1004-1]	
TC58NVG1S3HTA00@TSOP48 [CX1004-3]	
TC58NVG2S0FTA00@TSOP48 [CX1004-1]	
TC58NVG2S3ETA00@TSOP48 [CX1004-1]	
TC58NVG2S3ETAI0@TSOP48 [CX1004-3]	
TC58NVG3S0ETA00@TSOP48 [CX1004-1]	
TC58NVG3S0FTA00@TSOP48 [CX1004-3]	
TC58NVG4D2FTA00@TSOP48 [CX1004-1]	
TC58NVM9S3ETA00@TSOP48 [CX1004-1]	
TC89101(08bit) [CX0001]	TC89101(16bit) [CX0001]
TC89102(08bit) [CX0001]	TC89102(16bit) [CX0001]
TC89121 [CX0001]	TC89121@SOIC8 [CX1045]
TC89122 [CX0001]	TC89122@SOIC8 [CX1045]
TC97101 [CX0001]	TH50VPF5582ADSB@FBGA73 [CX5005]
TH50VPF5583ADSB@FBGA73 [CX5005]	TH50VPF5682CDSB@FBGA73 [CX5005]
TH50VPF5683CDSB@FBGA73 [CX5005]	TH50VPF5782AASB@FBGA73 [CX5057]
TH50VPF5783AASB@FBGA73 [CX5057]	TH50VPF6782AASB@FBGA73 [CX5057]
TH50VPF6783AASB@FBGA73 [CX5057]	TH50VSF1480AASB@FBGA65 [CX5057]
TH50VSF1481AASB@FBGA65 [CX5057]	TH50VSF2480AASB@FBGA65 [CX5057]
TH50VSF2481AASB@FBGA65 [CX5057]	TH50VSF2580AASB@FBGA69 [CX5057]
TH50VSF2581AASB@FBGA69 [CX5057]	TH50VSF2582AASB@FBGA69 [CX5057]
TH50VSF2582ADSB@FBGA73 [CX5005]	TH50VSF2582BDSB@FBGA73 [CX5005]
TH50VSF2583AASB@FBGA69 [CX5057]	TH50VSF2583ADSB@FBGA73 [CX5005]
TH50VSF2583BDSB@FBGA73 [CX5005]	TH50VSF2590AASB@FBGA69 [CX5001]
TH50VSF2682BDSB@FBGA73 [CX5005]	TH50VSF2683BDSB@FBGA73 [CX5005]
TH50VSF3580AASB@FBGA69 [CX5057]	TH50VSF3581AASB@FBGA69 [CX5057]
TH50VSF3582AASB@FBGA69 [CX5057]	TH50VSF3582BDSB@FBGA73 [CX5005]
TH50VSF3583AASB@FBGA69 [CX5057]	TH50VSF3583BDSB@FBGA73 [CX5005]
TH50VSF3680AASB@FBGA69 [CX5057]	TH50VSF3681AASB@FBGA69 [CX5057]
TH50VSF3682AASB@FBGA69 [CX5057]	TH50VSF3682BDSB@FBGA73 [CX5005]
TH50VSF3683AASB@FBGA69 [CX5057]	TH50VSF3683BDSB@FBGA73 [CX5005]
TH50VSF4682AASB@FBGA69 [CX5057]	TH50VSF4683AASB@FBGA69 [CX5057]
TH58DVG4S0ETAK0(1G)@TSOP48 [CX1004-1]	
TH58DVG5S0ETAK0(1G)@TSOP48 [CX1004-1]	
TH58NVG1S3AFT05@TSOP48 [CX1004]	TMM24128 [CX0001]
TMM24128A [CX0001]	TMM24128AP [CX0001]
TMM24256 [CX0001]	TMM24256A [CX0001]
TMM24256AP [CX0001]	TMM24256B [CX0001]
TMM24512 [CX0001]	TMM24512A [CX0001]
TMM24512P [CX0001]	TMM2464AP [CX0001]
TMM27128 [CX0001]	TMM27128A [CX0001]
TMM27128ADI [CX0001]	TMM27128AP [CX0001]
TMM27256 [CX0001]	TMM27256A [CX0001]
TMM27256AD [CX0001]	TMM27256ADI [CX0001]
TMM27256BD [CX0001]	TMM27256BDI [CX0001]

TMM27256D [CX0001]  
TMM2732 [CX0001]  
TMM2732D [CX0001]  
TMM27512AD [CX0001]  
TMM27512D [CX0001]  
TMM2764 [CX0001]  
TMM2764ADI [CX0001]  
TMM2764D [CX0001]  
TV00560002ADBB@FBGA73 [CX5196]  
TV00560002EDGB@FBGA81 [CX5196]  
TV00560003EDGB@FBGA81 [CX5196]  
TV00570002ADGB@FBGA85 [CX5196]  
TV00570002CDGB@FBGA81 (MW) [CX5005]  
TV00570003AABB@FBGA73 [CX5057]  
TV00570003CDGB@FBGA81 [CX5196]  
TV00670002CABB@FBGA73 [CX5196]  
TV00670002CDGB@FBGA81 [CX5196]  
TV00670003CABB@FBGA73 [CX5196]  
TV00670003CDGB@FBGA81 [CX5196]  
TY00570003ARGQ@FBGA52 [CX5131]  
TY00670003ARGQ@FBGA52 [CX5131]  
TY00680002ARGQ@FBGA52 [CX5131]  
TY00680003ARGQ@FBGA52 [CX5131]  
TY6701111184KC04@FBGA52 [CX5131]

TMM27256DI [CX0001]  
TMM2732A [CX0001]  
TMM27512 [CX0001]  
TMM27512ADI [CX0001]  
TMM27512DI [CX0001]  
TMM2764AD [CX0001]  
TMM2764AP [CX0001]  
TMM2764DI [CX0001]  
TV00560002DDGB@FBGA81 [CX5196]  
TV00560003ADBB@FBGA73 [CX5196]  
TV00570002AABB@FBGA73 [CX5057]  
TV00570002CDGB@FBGA81 [CX5196]  
TV00570003ADGB@FBGA85 [CX5196]  
TV00670002ADGB@FBGA81 [CX5196]  
TV00670002CAGB@FBGA73 [CX5196]  
TV00670003ADGB@FBGA81 [CX5196]  
TV00670003CAGB@FBGA73 [CX5196]  
TY00570002ARGQ@FBGA52 [CX5131]  
TY00670002ARGQ@FBGA52 [CX5131]  
TY00680002ADGB@FBGA81 [CX5196]  
TY00680003ADGB@FBGA81 [CX5196]  
TY5701111183KC04@FBGA52 [CX5131]

#### DRAM & SRAM

TC518128 [CX0001]  
TC518129 [CX0001]  
TC51832  
TC518512 [CX0001]  
TC551001FL [CX0001]  
TC551001PL [CX0001]  
TC55257 [CX0001]  
TC55257L [CX0001]  
TC55258 [CX0001]  
TC55258L [CX0001]  
TC55328 [CX0001]  
TC5563APL [CX0001]  
TC5564APL [CX0001]  
TC5565AFL [CX0001]  
TC5565APL [CX0001]  
TC5588 [CX0001]  
TC55B88 [CX0001]  
TMM2063 [CX0001]

TC518128@SOIC32 [CX1035]  
TC518129@SOIC32 [CX1035]  
TC51832@SOIC28 [CX1035]  
TC518512@SOIC32 [CX1035]  
TC551001FL@SOIC32 [CX1035]  
TC551001PL@SOIC32 [CX1035]  
TC55257@SOIC28 [CX1035]  
TC55257L@SOIC28 [CX1035]  
TC55258@SOIC28 [CX1035]  
TC55258L@SOIC28 [CX1035]  
TC55328@SOIC28 [CX1035]  
TC5563APL@SOIC28 [CX1035]  
TC5564APL@SOIC28 [CX1035]  
TC5565AFL@SOIC28 [CX1035]  
TC5565APL@SOIC28 [CX1035]  
TC5588@SOIC28 [CX1035]  
TC55B88@SOIC28 [CX1035]  
TMM2063@SOIC28 [CX1035]

#### MICROCONTROLLER

TMP47P201VP  
TMP47P202VP  
TMP47P206VP  
TMP47P241VMG@SOIC28 [CX1035]  
TMP47P241VNG@SDIP28 [CX0032]  
TMP47P403VMG@SOIC28 [CX1033]  
TMP47P403VNG@SDIP28 [CX0032]  
TMP47P422VFG@QFP44 [CX3004]  
TMP47P422VNG@SDIP42 [CX0042]  
TMP47P422VUG@QFP44 [CX3005]

TMP47P202VM@SOIC20 [CX1021]  
TMP47P206VM@SOIC20 [CX1021]  
TMP47P241VM@SOIC28 [CX1035]  
TMP47P241VN@SDIP28 [CX0032]  
TMP47P403VM@SOIC28 [CX1033]  
TMP47P403VN@SDIP28 [CX0032]  
TMP47P422VFG@QFP44 [CX3004]  
TMP47P422VN@SDIP42 [CX0042]  
TMP47P422VU@QFP44 [CX3005]  
TMP47P440VFG@QFN44 [CX3004]

TMP47P440VFG@QFN44 [CX3004]  
TMP47P440VNG@SDIP42 [CX0042]  
TMP47P443VMG@SOIC28 [CX1033]  
TMP47P443VNG@SDIP28 [CX0032]  
TMP68HC11E1@QFP52 [CX3010]  
TMP68HC11E9@QFP52 [CX3010]  
TMP86FH09ANG@SDIP32 [CX0032]  
TMP86FH46ANG@SDIP42 [CX0042]  
TMP86FH47ADUG@QFP48 [CX3007]  
TMP86FH47BUG@QFP44 [CX3005]  
TMP86FH92DMG@SSOP30 [CX1026]  
TMP86FS49AFG@QFP64 [CX3014]  
TMP86FS49AIUG@QFP64 [CX3011]  
TMP86FS49BFG@QFP64 [CX3014]  
TMP86P202M@SOIC20 [CX1031]  
TMP86P203M@SOIC20 [CX1031]  
TMP86P807M@SOP28 [CX1019]  
TMP86P807N@SDIP28 [CX0032]  
TMP86P808DM@SSOP30 [CX1026]  
TMP86P808N@SDIP30 [CX0032]  
TMP86PH06N@SDIP42 [CX0042]  
TMP86PH06U@QFP44 [CX3005]  
TMP86PH46N@SDIP42 [CX0042]  
TMP86PH47U@QFP44 [CX3005]  
TMP86PM29AF@QFP64 [CX3014]  
TMP86PM46N@SDIP42 [CX0042]  
TMP86PM47AU@QFP44 [CX3005]  
TMP86PM47U@QFP44 [CX3005]  
TMP86PM72F@QFP64 [CX3014]  
TMP86PM74AF@PQFP80 [CX3019]  
TMP86PM74F@PQFP80 [CX3019]  
TMP86PS44U@QFP44 [CX3005]  
TMP87P408M@SOIC28 [CX1035]  
TMP87P409M@SOIC28 [CX1035]  
TMP87P808LM@SOP28 [CX1035]  
TMP87P808M@SOP28 [CX1035]  
TMP87P809M@SOIC28 [CX1035]  
TMP87P844N@SDIP42 [CX0042]  
TMP87PH00DF@QFP64 [CX3014]  
TMP87PH00F@QFP64 [CX3015]  
TMP87PH00LF@QFP64 [CX3014]  
TMP87PH00N@SDIP64 [CX0064]  
TMP87PH20F@QFP80 [CX3019]  
TMP87PH40AF@PQFP64 [CX3015]  
TMP87PH40AN@SDIP64 [CX0064]  
TMP87PH46N@SDIP42 [CX0042]  
TMP87PH47LU@QFP44 [CX3005]  
TMP87PH47U@QFP44 [CX3005]  
TMP87PH48DF@LQFP64 [CX3014]  
TMP87PH48U@LQFP64 [CX3011]  
TMP87PM14F@QFP64 [CX3015]  
TMP87PM14N@SDIP64 [CX0064]  
TMP87PM20F@QFP80 [CX3019]  
TMP87PM29N@SDIP64 [CX0064]  
TMP87PM29U@LQFP64 [CX3011]  
TMP87PM40AF@PQFP64 [CX3015]  
TMP87PM40AN@SDIP64 [CX0064]  
TMP87PM41F@QFP64 [CX3015]  
TMP87PM41N@SDIP64 [CX0064]

TMP47P440VN@SDIP42 [CX0042]  
TMP47P443VM@SOIC28 [CX1033]  
TMP47P443VN@SDIP28 [CX0032]  
TMP68HC11E1@PLCC52 [CX2052]  
TMP68HC11E9@PLCC52 [CX2052]  
TMP68HC711E9@PLCC52 [CX2052]  
TMP86FH409NG@SDIP32 [CX0032]  
TMP86FH46BNG@SDIP42 [CX0042]  
TMP86FH47AUG@QFP44 [CX3005]  
TMP86FH809NG@SDIP32 [CX0032]  
TMP86FH92IDMG@SSOP30 [CX1026]  
TMP86FS49AIFG@QFP64 [CX3014]  
TMP86FS49AUG@QFP64 [CX3011]  
TMP86FS49BUG@QFP64 [CX3011]  
TMP86P202P  
TMP86P203P  
TMP86P807MG@SOP28 [CX1019]  
TMP86P807NG@SDIP28 [CX0032]  
TMP86P808DMG@SSOP30 [CX1026]  
TMP86P808NG@SDIP30 [CX0032]  
TMP86PH06NG@SDIP42 [CX0042]  
TMP86PH06UG@QFP44 [CX3005]  
TMP86PH46NG@SDIP42 [CX0042]  
TMP86PH47UG@QFP44 [CX3005]  
TMP86PM29AU@QFP64 [CX3011]  
TMP86PM46NG@SDIP42 [CX0042]  
TMP86PM47AUG@QFP44 [CX3005]  
TMP86PM47UG@QFP44 [CX3005]  
TMP86PM72FG@QFP64 [CX3014]  
TMP86PM74AFG@PQFP80 [CX3019]  
TMP86PM74FG@PQFP80 [CX3019]  
TMP86PS44UG@QFP44 [CX3005]  
TMP87P408N@SDIP28 [CX0032]  
TMP87P409N@SDIP28 [CX0032]  
TMP87P808LN@SDIP28 [CX0032]  
TMP87P808N@SDIP28 [CX0032]  
TMP87P809N@SDIP28 [CX0032]  
TMP87P844NG@SDIP42 [CX0042]  
TMP87PH00DFG@QFP64 [CX3014]  
TMP87PH00FG@QFP64 [CX3015]  
TMP87PH00LFG@QFP64 [CX3014]  
TMP87PH00NG@SDIP64 [CX0064]  
TMP87PH20FG@QFP80 [CX3019]  
TMP87PH40AFG@PQFP64 [CX3015]  
TMP87PH40ANG@SDIP64 [CX0064]  
TMP87PH46NG@SDIP42 [CX0042]  
TMP87PH47LUG@QFP44 [CX3005]  
TMP87PH47UG@QFP44 [CX3005]  
TMP87PH48DFG@LQFP64 [CX3014]  
TMP87PH48UG@LQFP64 [CX3011]  
TMP87PM14FG@QFP64 [CX3015]  
TMP87PM14NG@SDIP64 [CX0064]  
TMP87PM20FG@QFP80 [CX3019]  
TMP87PM29NG@SDIP64 [CX0064]  
TMP87PM29UG@LQFP64 [CX3011]  
TMP87PM40AFG@PQFP64 [CX3015]  
TMP87PM40ANG@SDIP64 [CX0064]  
TMP87PM41FG@QFP64 [CX3015]  
TMP87PM41NG@SDIP64 [CX0064]

TMP87PM41U@LQFP64 [CX3011]	TMP87PM41UG@LQFP64 [CX3011]
TMP87PM43N@SDIP42 [CX0042]	TMP87PM43NG@SDIP42 [CX0042]
TMP87PM48DF@LQFP64 [CX3014]	TMP87PM48DFG@LQFP64 [CX3014]
TMP87PM48U@LQFP64 [CX3011]	TMP87PM48UG@LQFP64 [CX3011]
TMP87PM53F@PQFP80 [CX3019]	TMP87PM53FG@PQFP80 [CX3019]
TMP87PM70F@QFP80 [CX3019]	TMP87PM70FG@QFP80 [CX3019]
TMP87PM74F@QFP80 [CX3019]	TMP87PM74FG@QFP80 [CX3019]
TMP87PM75F@QFP100 [CX3023]	TMP87PM75FG@QFP100 [CX3023]
TMP87PM78F@QFP100 [CX3023]	TMP87PM78FG@QFP100 [CX3023]
TMP87PP21DF@QFP80 [CX3016]	TMP87PP21DFG@QFP80 [CX3016]
TMP87PP21F@PQFP80 [CX3019]	TMP87PP21FG@QFP80 [CX3016]
TMP87PP23F@PQFP100 [CX3023]	TMP87PP23FG@PQFP100 [CX3023]
TMP87PP24AF@QFP100 [CX3021]	TMP87PP24AFG@QFP100 [CX3021]
TMP87PP24F@QFP100 [CX3021]	TMP87PP24FG@QFP100 [CX3021]
TMP87PP71F@PQFP80 [CX3019]	TMP87PP71FG@PQFP80 [CX3019]
TMP87PS64F@PQFP100 [CX3023]	TMP87PS64FG@PQFP100 [CX3023]
TMP87PS68F@QFP80 [CX3016]	TMP87PS68FG@QFP80 [CX3016]
TMP87PS71AF@PQFP80 [CX3019]	TMP87PS71AFG@PQFP80 [CX3019]
TMP87PS71F@PQFP80 [CX3019]	TMP87PS71FG@PQFP80 [CX3019]
TMP88FH41UG@QFP44 [CX3005]	TMP88FW45AFG@PQFP80 [CX3019]
TMP88FW45FG@PQFP80 [CX3019]	TMP88PH40M@SOIC28 [CX1064]
TMP88PH40MG@SOIC28 [CX1064]	TMP88PH40N@SDIP28 [CX0032]
TMP88PH40NG@SDIP28 [CX0032]	TMP88PS42F@PQFP64 [CX3015]
TMP88PS42FG@PQFP64 [CX3015]	TMP88PS42N@SDIP64 [CX0064]
TMP88PS42NG@SDIP64 [CX0064]	TMP89FH42UG@QFP44 [CX3003]
TMP89FM42UG@QFP44 [CX3003]	TMP89FM82DUG@QFP48 [CX3007]
TMP91FU62DFG@PQFP80 [CX3019]	TMP91FU62FG@QFP80 [CX3016]
TMP91PW10F@QFP100 [CX3021]	TMP91PW10FG@QFP100 [CX3021]
TMP91PW11F@QFP100 [CX3021]	TMP91PW11FG@QFP100 [CX3021]
TMP91PW12F@QFP100 [CX3021]	TMP91PW12FG@QFP100 [CX3021]
TMP91PW18AF@PQFP80 [CX3019]	TMP91PW18AFG@PQFP80 [CX3019]
TMP93PS40DF@QFP100 [CX3021]	TMP93PS40DFG@QFP100 [CX3021]
TMP93PS40F@QFP100 [CX3021]	TMP93PS40FG@QFP100 [CX3021]
TMP93PS44F@QFP80 [CX3016]	TMP93PS44FG@QFP80 [CX3016]
TMP93PW20AF@QFP144 [CX3034]	TMP93PW20AFG@QFP144 [CX3034]
TMP93PW32F@QFP64 [CX3014]	TMP93PW32FG@QFP64 [CX3014]
TMP93PW40DF@QFP100 [CX3021]	TMP93PW40DFG@QFP100 [CX3021]
TMP93PW44ADF@PQFP80 [CX3019]	TMP93PW44ADFG@PQFP80 [CX3019]
TMP93PW46AF@QFP100 [CX3021]	TMP93PW46AFG@QFP100 [CX3021]
TMP95PW64F@QFP100 [CX3021]	TMP95PW64FG@QFP100 [CX3021]
TMP96PM40F@PQFP80 [CX3019]	TMP96PM40FG@PQFP80 [CX3019]

## TOSHIBA-CUSTOMER

### E (E) PROM/FRAM/NVRAM

TC58NVG0S3ETA00 (New)@TSOP48 [CX1004-3]

## TURBO IC

### E (E) PROM/FRAM/NVRAM

TU24C01 [CX0001]	TU24C01@SOIC8 [CX1045]
TU24C02 [CX0001]	TU24C02@SOIC8 [CX1045]
TU24C04 [CX0001]	TU24C04@SOIC8 [CX1045]
TU24C08 [CX0001]	TU24C08@SOIC8 [CX1045]
TU24C128 [CX0001]	TU24C128@SOIC8 [CX1045]

TU24C16 [CX0001]  
TU24C16@TSSOP8 [CX1059]  
TU24C256@SOIC8 [CX1045]  
TU24C32@SOIC8 [CX1045]  
TU24C64@SOIC8 [CX1045]

TU24C16@SOIC8 [CX1045]  
TU24C256 [CX0001]  
TU24C32 [CX0001]  
TU24C64 [CX0001]

## UBICOM

### MICROCONTROLLER

SX20AC/SS/G@SSOP20 [CX1026]  
SX28AC/DP [CX0001]  
SX28AC/SS/G@SSOP28 [CX1026]  
SX48BD/G@TQFP48 [CX3047]

SX20AC/SS@SSOP20 [CX1026]  
SX28AC/DP/G [CX0001]  
SX28AC/SS@SSOP28 [CX1026]  
SX48BD@TQFP48 [CX3047]

## UMC

### E (E) PROM/FRAM/NVRAM

2732 [CX0001]

2764 [CX0001]

### DRAM & SRAM

UM61256 [CX0001]  
UM61512 [CX0001]  
UM6164 [CX0001]  
UM621024 [CX0001]  
UM62256 [CX0001]  
UM62256A [CX0001]  
UM6264 [CX0001]  
UM6264A [CX0001]

UM61256@SOIC28 [CX1035]  
UM61512@SOIC32 [CX1035]  
UM6164@SOIC28 [CX1035]  
UM621024@SOIC32  
UM62256@SOIC28 [CX1035]  
UM62256A@SOIC28 [CX1035]  
UM6264@SOIC28 [CX1035]  
UM6264A@SOIC28 [CX1035]

## UNIGEN

### E (E) PROM/FRAM/NVRAM

UG24C01 [CX0001]  
UG24C01@TSSOP8 [CX1059]  
UG24C02@SOP8 [CX1045]  
UG24C04 [CX0001]  
UG24C04@TSSOP8 [CX1059]  
UG24C08@SOP8 [CX1045]  
UG24C16 [CX0001]  
UG24C16@TSSOP8 [CX1059]

UG24C01@SOP8 [CX1045]  
UG24C02 [CX0001]  
UG24C02@TSSOP8 [CX1059]  
UG24C04@SOP8 [CX1045]  
UG24C08 [CX0001]  
UG24C08@TSSOP8 [CX1059]  
UG24C16@SOP8 [CX1045]

## VANTIS

### PLD

M4-128/64@PQFP100 [CX3022]  
M4-128N/64@PLCC84 [CX2084]  
M4LV-128/64@TQFP100 [CX3021]  
M4LV-64/32@PLCC44 [CX2044]  
M4LV-64/32@TQFP48 [CX3007]

M4-128/64@TQFP100 [CX3021]  
M4LV-128/64@PQFP100 [CX3022]  
M4LV-128N/64@PLCC84 [CX2084]  
M4LV-64/32@TQFP44 [CX3003]  
MACH110@PLCC44 [CX2044]

MACH111@PLCC44 [CX2044]  
MACH130@PLCC84 [CX2084]  
MACH131@PLCC84 [CX2084]  
MACH131SP@TQFP100 [CX3021]  
MACH210@TQFP44 [CX3003]  
MACH210A@TQFP44 [CX3003]  
MACH210AQ@TQFP44 [CX3003]  
MACH220@PLCC68 [CX2068]  
MACH231SP@PLCC84 [CX2084]  
MACH231SP@TQFP100 [CX3021]  
MACH436@PLCC84 [CX2084]  
MACH446@TQFP100 [CX3021]  
MACHLV210@TQFP44 [CX3003]  
MACHLV446@PQFP100 [CX3022]  
PAL29M16H [CX0001]  
PALCE20RA10@PLCC28 [CX2028]  
PALCE20RA10H [CX0001]  
PALCE20RA10H@SOIC24 [CX1033]  
PALCE20RA10Q@PLCC28 [CX2028]  
PALCE26V12H/4 [CX0001]  
PALCE26V12H/4@SOIC28 [CX1033]  
PALCE26V12H-15@PLCC28 [CX0001]  
PALCE26V12H-20 [CX0001]  
PALCE26V12H-20@SOIC28 [CX0001]  
PALCE26V12H-25@PLCC28 [CX0001]  
PALCE29M16H [CX0001]  
PALCE29M16H@SOIC24 [CX1033]  
PALCE29MA16H@PLCC28 [CX2028]  
PALCE610 [CX0001]  
PALCE610@SOIC24 [CX1003]  
PALCE610H@PLCC28 [CX2028]  
PALCE630H [CX0001]  
PALCE630H@SOIC24 [CX1003]

MACH111@TQFP44 [CX3003]  
MACH131/1@PLCC84 [CX2084]  
MACH131SP@PQFP100 [CX3022]  
MACH210@PLCC44 [CX2044]  
MACH210A@PLCC44 [CX2044]  
MACH210AQ@PLCC44 [CX2044]  
MACH211@PLCC44 [CX2044]  
MACH221@PLCC68 [CX2068]  
MACH231SP@PQFP100 [CX3022]  
MACH435@PLCC84 [CX2084]  
MACH446@PQFP100 [CX3022]  
MACHLV210@PLCC44 [CX2044]  
MACHLV436@PLCC84 [CX2084]  
MACHLV446@TQFP100 [CX3021]  
PALCE20RA10 [CX0001]  
PALCE20RA10@SOIC24 [CX1033]  
PALCE20RA10H@PLCC28 [CX2028]  
PALCE20RA10Q [CX0001]  
PALCE20RA10Q@SOIC24 [CX1033]  
PALCE26V12H/4@PLCC28 [CX2028]  
PALCE26V12H-15 [CX0001]  
PALCE26V12H-15@SOIC28 [CX0001]  
PALCE26V12H-20@PLCC28 [CX0001]  
PALCE26V12H-25 [CX0001]  
PALCE26V12H-25@SOIC28 [CX0001]  
PALCE29M16H@PLCC28 [CX2028]  
PALCE29MA16H [CX0001]  
PALCE29MA16H@SOIC24 [CX1033]  
PALCE610@PLCC28 [CX2028]  
PALCE610H [CX0001]  
PALCE610H@SOIC24 [CX1003]  
PALCE630H@PLCC28 [CX2028]

## VERSACHIPS

### MICROCONTROLLER

V87C54 [CX0001]  
V87C54@TQFP44 [CX3003]  
V87C58@PLCC44 [CX2044]

V87C54@PLCC44 [CX2044]  
V87C58 [CX0001]  
V87C58@TQFP44 [CX3003]

## VLSI

### E (E) PROM / FRAM / NVRAM

VT27C128 [CX0001]  
VT27C512 [CX0001]  
VT28H64 [CX0001]

VT27C256 [CX0001]  
VT27C64 [CX0001]  
VT28HC64 [CX0001]

### PLD

GAL16V8 [CX0001]

## WELTREND

## MICROCONTROLLER

WT61P4K420@SDIP42 [CX0042]	WT61P4K421@SDIP42 [CX0042]
WT61P4K422@SDIP42 [CX0042]	WT61P4L440@PLCC44 [CX2044]
WT61P4N400 [CX0001]	WT61P4N401 [CX0001]
WT61P6K420@SDIP42 [CX0042]	WT61P6L440@PLCC44 [CX2044]
WT61P6L441@PLCC44 [CX2044]	WT61P6S@TQFP44 [CX3003]
WT61P7@LQFP44 [CX3003]	WT61P7@PLCC44 [CX2044]
WT61P7@TQFP48 [CX3007]	WT61P8@TQFP44 [CX3003]
WT61P8S@TQFP44 [CX3003]	WT62P1-K42@SDIP42 [CX0042]
WT62P1-N28(dip28) [CX0001]	WT62P1-N40(dip40) [CX0001]
WT62P1-N42(dip42) [CX0001]	WT62P1-S44@PSOP44 [CX1014]
WT62P2-K42@SDIP42 [CX0042]	WT62P2-L44@PLCC44 [CX2044]
WT62P2-N40(dip40) [CX0001]	WT62P2-N42(dip42) [CX0001]
WT62P2-S44@PSOP44 [CX1014]	WT6702F@SOP16 [CX1016]
WT6702F@SOP20 [CX1033]	WT6702F@SOP24 [CX1033]
WT6702F@SSOP20 [CX1025]	WT6703F@SOP20 [CX1033]
WT6703F@SOP24 [CX1033]	WT6703F@SOP28 [CX1033]
WT6703F@SSOP20 [CX1025]	WT6703F@SSOP24 [CX1025]
WT6703FS161@SSOP16 [CX1016]	WT6703FS163@SSOP16 [CX1016]

## WHITE ELECTRONIC DESIGNS

### E (E) PROM/FRAM/NVRAM

WE128K8 [CX0001]	WE256K8 [CX0001]
WE512K8 [CX0001]	WF256K8 [CX0001]
WF256K8@CLCC32 [CX2032]	WF256K8@CSOJ32 [CX1038]
WF512K8 [CX0001]	WF512K8@CLCC32 [CX2032]
WF512K8@CSOJ32 [CX1038]	WME128K8 [CX0001]
WME128K8@CLCC32 [CX2032]	WME128K8@CSOJ32 [CX1038]
WMF128K8 [CX0001]	WMF128K8@CLCC32 [CX2032]
WMF128K8@CSOJ32 [CX1038]	WMF256K8 [CX0001]
WMF256K8@CLCC32 [CX2032]	WMF256K8@CSOJ32 [CX1038]
WMF512K8 [CX0001]	WMF512K8@CLCC32 [CX2032]
WMF512K8@CSOJ32 [CX1038]	WMS128K8 [CX0001]
WMS128K8@CLCC32 [CX2032]	WMS128K8@CSOJ32 [CX1038]
WMS256K8 [CX0001]	WMS256K8@CLCC32 [CX2032]
WMS256K8@CSOJ32 [CX1038]	WMS512K8 [CX0001]
WMS512K8@CLCC32 [CX2032]	WMS512K8@CSOJ32 [CX1038]

## WINBOND

### E (E) PROM/FRAM/NVRAM

W19B160BBB@FBGA48 [CX5002]	W19B160BBT@TSOP48 [CX1004]
W19B160BTB@FBGA48 [CX5002]	W19B160BTT@TSOP48 [CX1004]
W19B320ABB@FBGA48 [CX5001]	W19B320ABT@TSOP48 [CX1004]
W19B320ATB@FBGA48 [CX5001]	W19B320ATT@TSOP48 [CX1004]
W19B320BBB@FBGA48 [CX5001]	W19B320BBT@TSOP48 [CX1004]
W19B320BTB@FBGA48 [CX5001]	W19B320BTT@TSOP48 [CX1004]
W19B320SBB@FBGA48 [CX5001]	W19B320SBT@TSOP48 [CX1004]
W19B320STB@FBGA48 [CX5001]	W19B320STT@TSOP48 [CX1004]
W19B322MBB@FBGA48 [CX5001]	W19B322MBT@TSOP48 [CX1004]
W19B322MTB@FBGA48 [CX5001]	W19B322MTT@TSOP48 [CX1004]
W19B323MBB@FBGA48 [CX5001]	W19B323MBT@TSOP48 [CX1004]



W19B323MTB@FBGA48 [CX5001]	W19B323MTT@TSOP48 [CX1004]
W19B324MBB@FBGA48 [CX5001]	W19B324MBT@TSOP48 [CX1004]
W19B324MTB@FBGA48 [CX5001]	W19B324MTT@TSOP48 [CX1004]
W19L320SBB@FBGA48 [CX5001]	W19L320SBT@TSOP48 [CX1004]
W19L320STB@FBGA48 [CX5001]	W19L320STT@TSOP48 [CX1004]
W25B40(Bottom Boot)@MLP8 [CX4005#1]	
W25B40(Bottom Boot)@SOIC8 [CX1045#1]	
W25B40(Top Boot)@MLP8 [CX4005#1]	
W25B40(Top Boot)@SOIC8 [CX1045#1]	
W25B40A(Bottom Boot)@MLP8 [CX4005#1]	
W25B40A(Bottom Boot)@SOIC8 [CX1045#1]	
W25B40A(Top Boot)@MLP8 [CX4005#1]	
W25B40A(Top Boot)@SOIC8 [CX1045#1]	
W25D10 [CX0001]	W25D10(SN)@SOIC8 [CX1045]
W25D10(SS)@SOIC8 [CX1044]	W25D10(ZP)@WSON8 [CX4005]
W25D16@SOIC16 [CX1033#1]	W25D16@SOIC8 [CX1044#1]
W25D20 [CX0001]	W25D20(SN)@SOIC8 [CX1045]
W25D20(SS)@SOIC8 [CX1044]	W25D20(ZP)@WSON8 [CX4005]
W25D40 [CX0001]	W25D40(SN)@SOIC8 [CX1045]
W25D40(SS)@SOIC8 [CX1044]	W25D40(ZP)@WSON8 [CX4005]
W25D80 [CX0001]	W25D80(SN)@SOIC8 [CX1045]
W25D80(SS)@SOIC8 [CX1044]	W25D80(ZP)@WSON8 [CX4005]
W25P10@MLP8 [CX4005]	W25P10@SOIC8 [CX1045]
W25P16@MLP8 [CX4005#1]	W25P16@MLP8(ISP) [CX0001]
W25P16@SOIC16 [CX1033#1]	W25P16@SOIC16(ISP) [CX0001]
W25P16@SOIC8 [CX1044#1]	W25P16@SOIC8(ISP) [CX0001]
W25P20@MLP8 [CX4005#1]	W25P20@SOIC8 [CX1045#1]
W25P32@MLP8 [CX4005#1]	W25P32@MLP8(ISP) [CX0001]
W25P32@SOIC16 [CX1033#1]	W25P32@SOIC16(ISP) [CX0001]
W25P40@MLP8 [CX4005#1]	W25P40@SOIC8 [CX1045#1]
W25P64@MLP8 [CX4005#1]	W25P64@MLP8(ISP) [CX0001]
W25P64@SOIC16 [CX1033#1]	W25P64@SOIC16(ISP) [CX0001]
W25P80@MLP8 [CX4005#1]	W25P80@SOIC8 [CX1045#1]
W25Q05CV-SD8 [CX1059]	W25Q05CV-SN8 [CX1045]
W25Q05CV-UX8 [CX4002]	W25Q05CV-ZP8 [CX4005]
W25Q10CV-SD8 [CX1059]	W25Q10CV-SN8 [CX1045]
W25Q10CV-UX8 [CX4002]	W25Q10CV-ZP8 [CX4005]
W25Q128BV@SOIC16 [CX1033#1]	W25Q128BV@WSON8 [CX4006#1]
W25Q128FV [CX0001#1]	W25Q128FV@SOIC16 [CX1033#1]
W25Q128FV@SOIC8 [CX1044#1]	W25Q128FV@SON8 [CX4005#1]
W25Q128FV@TFBGA24[5*5] [CX5157]	W25Q128FV@TFBGA24[6*4] [CX5146]
W25Q128FV@VSOP8 [CX1044#1]	W25Q128FV@WSON8 [CX4006#1]
W25Q16@MLP8 [CX4005#1]	W25Q16@MLP8(ISP) [CX0001]
W25Q16@SOIC16 [CX1033#1]	W25Q16@SOIC16(ISP) [CX0001]
W25Q16@SOIC8 [CX1044#1]	W25Q16@SOIC8(ISP) [CX0001]
W25Q16BV [CX0001#1]	W25Q16BV(SF)@SOIC16 [CX1033#1]
W25Q16BV(SN)@SOIC8 [CX1045#1]	W25Q16BV(SS)@SOIC8 [CX1044#1]
W25Q16BV(ZP)@WSON8 [CX4005#1]	W25Q16CL [CX0001]
W25Q16CL(SF)@SOIC16 [CX1033#1]	W25Q16CL(SN)@SOIC8 [CX1045#1]
W25Q16CL(SS)@SOIC8 [CX1044#1]	W25Q16CL(ZP)@WSON8 [CX4005#1]
W25Q16CV(SF)@SOIC16 [CX1033#1]	W25Q16CV(SN)@SOIC8 [CX1045#1]
W25Q16CV(SS)@SOIC8 [CX1044#1]	W25Q16CV(ZP)@WSON8 [CX4005#1]
W25Q16CV@TFBGA24 [CX5146]	W25Q16DV(SF)@SOIC16 [CX1033#1]
W25Q16DV(SN)@SOIC8 [CX1045#1]	W25Q16DV(SS)@SOIC8 [CX1044#1]
W25Q16DV(ZP)@WSON8 [CX4005#1]	W25Q16DV@TFBGA24 [CX5146]
W25Q16DW(SF)@SOIC16 [CX1033#1]	W25Q16DW(SN)@SOIC8 [CX1045#1]
W25Q16DW(SS)@SOIC8 [CX1044#1]	W25Q16DW(ZP)@WSON8 [CX4005#1]
W25Q16DW@TFBGA24 [CX5146]	W25Q16V(SF)@SOIC16 [CX1033#1]
W25Q16V(SS)@SOIC8 [CX1044#1]	W25Q16V(ZP)@WSON8 [CX4005#1]

W25Q20BW-SN8 [CX1045]  
W25Q20BW-UX8 [CX4002]  
W25Q20CV-SN8 [CX1045]  
W25Q20CV-ZP8 [CX4005]  
W25Q256FV@TFBGA24[5\*5] [CX5157]  
W25Q258FV@TFBGA24[6\*4] [CX5146]  
W25Q32@MLP8(ISP) [CX0001]  
W25Q32@SOIC16(ISP) [CX0001]  
W25Q32BV(SF)@SOIC16 [CX1033#1]  
W25Q32BV(ZP)@WSON8 [CX4005#1]  
W25Q32BW(SN)@SOIC8 [CX1045#1]  
W25Q32BW(ZP)@WSON8 [CX4005#1]  
W25Q32DW(SN)@SOIC8 [CX1045#1]  
W25Q32DW(ZE)@WSON8 [CX4006#1]  
W25Q32FV [CX0001]  
W25Q32FV(SS)@SOIC8 [CX1044#1]  
W25Q32FV(ZE)@WSON8 [CX4006#1]  
W25Q32FV@TFBGA24[5\*5] [CX5157]  
W25Q32V(SF)@SOIC16 [CX1033#1]  
W25Q32V(ZP)@WSON8 [CX4005#1]  
W25Q40BL-SN8 [CX1045]  
W25Q40BL-SV8 [CX1045]  
W25Q40BL-ZP8 [CX4005]  
W25Q40BV-SN8 [CX1045]  
W25Q40BV-SV8 [CX1045]  
W25Q40BV-ZP8 [CX4005]  
W25Q40BW-SS8 [CX1044]  
W25Q40BW-UX8 [CX4002]  
W25Q40CV [CX0001]  
W25Q40CV-SS8 [CX1044]  
W25Q40CV-UX8 [CX4002]  
W25Q64BV [CX0001]  
W25Q64BV(SF)@SOIC16(ISP) [CX0001]  
W25Q64BV(SS)@SOIC8 [CX1044#1]  
W25Q64BV(ZE)@WSON8 [CX4006#1]  
W25Q64CV(SF)@SOIC16 [CX1033#1]  
W25Q64CV(ZE)@WSON8 [CX4006#1]  
W25Q64DW(SF)@SOIC16 [CX1033#1]  
W25Q64DW(ZE)@WSON8 [CX4006#1]  
W25Q64DW@TFBGA24 [CX5146]  
W25Q64FV(SF)@SOIC16 [CX1033#1]  
W25Q64FV(ST)@SOIC8 [CX1044#1]  
W25Q64FV(ZP)@WSON8 [CX4005#1]  
W25Q64FV@TFBGA24(5\*5) [CX5157]  
W25Q80@SOIC8 [CX1045#1]  
W25Q80BL@SOIC16 [CX1033#1]  
W25Q80BL@SOIC8(150mil) [CX1045#1]  
W25Q80BL@SOIC8(200mil) [CX1044#1]  
W25Q80BL@USON8 [CX4005#1]  
W25Q80BL@VSOP8(150mil) [CX1045#1]  
W25Q80BL@VSOP8(200mil) [CX1044#1]  
W25Q80BL@WSON8 [CX4005#1]  
W25Q80BV@SOIC16 [CX1033#1]  
W25Q80BV@SOIC8[5.4] [CX1044#1]  
W25Q80BW [CX0001]  
W25Q80BW@SOIC8[4.0] [CX1045#1]  
W25Q80BW@USON8 [CX4005#1]  
W25Q80BW@VSOP8[5.4] [CX1044#1]  
W25Q80DW [CX0001]

W25Q20BW-SV8 [CX1045]  
W25Q20BW-ZP8 [CX4005]  
W25Q20CV-UX8 [CX4002]  
W25Q256FV@SOIC16 [CX1033#1]  
W25Q256FV@WSON8 [CX4006#1]  
W25Q32@MLP8 [CX4005#1]  
W25Q32@SOIC16 [CX1033#1]  
W25Q32BV [CX0001#1]  
W25Q32BV(SS)@SOIC8 [CX1044#1]  
W25Q32BW(SF)@SOIC16 [CX1033#1]  
W25Q32BW(SS)@SOIC8 [CX1044#1]  
W25Q32DW(SF)@SOIC16 [CX1033#1]  
W25Q32DW(SS)@SOIC8 [CX1044#1]  
W25Q32DW(ZP)@WSON8 [CX4005#1]  
W25Q32FV(SF)@SOIC16 [CX1033#1]  
W25Q32FV(ST)@SOIC8 [CX1044#1]  
W25Q32FV(ZP)@WSON8 [CX4005#1]  
W25Q32FV@TFBGA24[6\*4] [CX5146]  
W25Q32V(SS)@SOIC8 [CX1044#1]  
W25Q40BL [CX0001]  
W25Q40BL-SS8 [CX1044]  
W25Q40BL-UX8 [CX4002]  
W25Q40BV [CX0001]  
W25Q40BV-SS8 [CX1044]  
W25Q40BV-UX8 [CX4002]  
W25Q40BW-SN8 [CX1045]  
W25Q40BW-SV8 [CX1045]  
W25Q40BW-ZP8 [CX4005]  
W25Q40CV-SN8 [CX1045]  
W25Q40CV-SV8 [CX1045]  
W25Q40CV-ZP8 [CX4005]  
W25Q64BV(SF)@SOIC16 [CX1033#1]  
W25Q64BV(SS)@SOIC8(ISP) [CX0001]  
W25Q64BV(ZE)@WSON8(ISP) [CX0001]  
W25Q64CV(SS)@SOIC8 [CX1044#1]  
W25Q64CV@TFBGA24 [CX5146]  
W25Q64DW(SS)@SOIC8 [CX1044#1]  
W25Q64DW(ZP)@WSON8 [CX4005#1]  
W25Q64FV [CX0001]  
W25Q64FV(SS)@SOIC8 [CX1044#1]  
W25Q64FV(ZE)@WSON8 [CX4006#1]  
W25Q64FV@TFBGA24(4\*6) [CX5146]  
W25Q80@MLP8 [CX4005#1]  
W25Q80BL [CX0001]  
W25Q80BV [CX0001]  
W25Q80BV@SOIC8[4.0] [CX1045#1]  
W25Q80BV@WSON8 [CX4005#1]  
W25Q80BW@SOIC16 [CX1033#1]  
W25Q80BW@SOIC8[5.4] [CX1044#1]  
W25Q80BW@VSOP8[4.0] [CX1045#1]  
W25Q80BW@WSON8 [CX4005#1]  
W25Q80DW@SOIC16 [CX1033#1]

W25Q80DW@SOIC8[4.0] [CX1045#1]  
W25Q80DW@USON8 [CX4005#1]  
W25Q80DW@VSOP8[5.4] [CX1044#1]  
W25X05CL-SD8 [CX1059]  
W25X05CL-UX8 [CX4002]  
W25X10 [CX0001]  
W25X10(SS)@SOIC8 [CX1044]  
W25X10AL [CX0001]  
W25X10AL(SS)@SOIC8 [CX1044]  
W25X10AV [CX0001]  
W25X10AV(SS)@SOIC8 [CX1044]  
W25X10BL [CX0001]  
W25X10BL(SS)@SOIC8 [CX1044]  
W25X10BV [CX0001]  
W25X10BV(SS)@SOIC8 [CX1044]  
W25X10BV-SD8 [CX1059]  
W25X10BV-UX8 [CX4002]  
W25X10CL(ZP)@WSON8 [CX4005]  
W25X10CL-UX8 [CX4002]  
W25X10L(SN)@SOIC8 [CX1045]  
W25X10V [CX0001]  
W25X10V(SS)@SOIC8 [CX1044]  
W25X16@SOIC16 [CX1033#1]  
W25X16@SOIC8 [CX1044#1]  
W25X16AL [CX0001#1]  
W25X16AL(SN)@SOIC8 [CX1045#1]  
W25X16AL(ZP)@WSON8 [CX4005#1]  
W25X16AV(SF)@SOIC16 [CX1033#1]  
W25X16AV(SS)@SOIC8 [CX1044#1]  
W25X16BV [CX0001#1]  
W25X16BV(SN)@SOIC8 [CX1045#1]  
W25X16BV(ZP)@WSON8 [CX4005#1]  
W25X16V(SF)@SOIC16 [CX1033#1]  
W25X16V(ZP)@WSON8 [CX4005#1]  
W25X20(SN)@SOIC8 [CX1045]  
W25X20(ZP)@WSON8 [CX4005]  
W25X20AL(SN)@SOIC8 [CX1045]  
W25X20AL(ZP)@WSON8 [CX4005]  
W25X20AV(SN)@SOIC8 [CX1045]  
W25X20AV(ZP)@WSON8 [CX4005]  
W25X20BL(SN)@SOIC8 [CX1045]  
W25X20BL(ZP)@WSON8 [CX4005]  
W25X20BL-UX8 [CX4002]  
W25X20BV(SN)@SOIC8 [CX1045]  
W25X20BV(ZP)@WSON8 [CX4005]  
W25X20CL(SN)@SOIC8 [CX1045]  
W25X20CL-SV8 [CX1045]  
W25X20CV-SN8 [CX1045]  
W25X20CV-UX8 [CX4002]  
W25X20L [CX0001]  
W25X20L(ZP)@WSON8 [CX4005]  
W25X20V(SN)@SOIC8 [CX1045]  
W25X20V(ZP)@WSON8 [CX4005]  
W25X32@SOIC16 [CX1033#1]  
W25X32@SOIC8 [CX1044#1]  
W25X32AV(SF)@SOIC16 [CX1033#1]  
W25X32AV(ZP)@WSON8 [CX4005#1]  
W25X32V(SS)@SOIC8 [CX1044#1]  
W25X40 [CX0001]  
W25Q80DW@SOIC8[5.4] [CX1044#1]  
W25Q80DW@VSOP8[4.0] [CX1045#1]  
W25Q80DW@WSON8 [CX4005#1]  
W25X05CL-SN8 [CX1045]  
W25X05CL-ZP8 [CX4005]  
W25X10(SN)@SOIC8 [CX1045]  
W25X10(ZP)@WSON8 [CX4005]  
W25X10AL(SN)@SOIC8 [CX1045]  
W25X10AL(ZP)@WSON8 [CX4005]  
W25X10AV(SN)@SOIC8 [CX1045]  
W25X10AV(ZP)@WSON8 [CX4005]  
W25X10BL(SN)@SOIC8 [CX1045]  
W25X10BL(ZP)@WSON8 [CX4005]  
W25X10BV(SN)@SOIC8 [CX1045]  
W25X10BV(ZP)@WSON8 [CX4005]  
W25X10BV-SV8 [CX1045]  
W25X10CL(SN)@SOIC8 [CX1045]  
W25X10CL-SD8 [CX1059]  
W25X10L [CX0001]  
W25X10L(ZP)@WSON8 [CX4005]  
W25X10V(SN)@SOIC8 [CX1045]  
W25X10V(ZP)@WSON8 [CX4005]  
W25X16@SOIC16(ISP) [CX0001]  
W25X16@SOIC8(ISP) [CX0001]  
W25X16AL(SF)@SOIC16 [CX1033#1]  
W25X16AL(SS)@SOIC8 [CX1044#1]  
W25X16AV [CX0001#1]  
W25X16AV(SN)@SOIC8 [CX1045#1]  
W25X16AV(ZP)@WSON8 [CX4005#1]  
W25X16BV(SF)@SOIC16 [CX1033#1]  
W25X16BV(SS)@SOIC8 [CX1044#1]  
W25X16V [CX0001#1]  
W25X16V(SS)@SOIC8 [CX1044#1]  
W25X20 [CX0001]  
W25X20(SS)@SOIC8 [CX1044]  
W25X20AL [CX0001]  
W25X20AL(SS)@SOIC8 [CX1044]  
W25X20AV [CX0001]  
W25X20AV(SS)@SOIC8 [CX1044]  
W25X20BL [CX0001]  
W25X20BL(SS)@SOIC8 [CX1044]  
W25X20BL-SV8 [CX1045]  
W25X20BV [CX0001]  
W25X20BV(SS)@SOIC8 [CX1044]  
W25X20BV-UX8 [CX4002]  
W25X20CL(ZP)@WSON8 [CX4005]  
W25X20CL-UX8 [CX4002]  
W25X20CV-SV8 [CX1045]  
W25X20CV-ZP8 [CX4005]  
W25X20L(SN)@SOIC8 [CX1045]  
W25X20V [CX0001]  
W25X20V(SS)@SOIC8 [CX1044]  
W25X21CL@SOIC8 [CX1045]  
W25X32@SOIC16(ISP) [CX0001]  
W25X32@SOIC8(ISP) [CX0001]  
W25X32AV(SS)@SOIC8 [CX1044#1]  
W25X32V(SF)@SOIC16 [CX1033#1]  
W25X32V(ZP)@WSON8 [CX4005#1]  
W25X40(SN)@SOIC8 [CX1045]

W25X40(SS)@SOIC8 [CX1044]  
W25X40AL [CX0001]  
W25X40AL(SS)@SOIC8 [CX1044]  
W25X40AV [CX0001]  
W25X40AV(SS)@SOIC8 [CX1044]  
W25X40BL [CX0001]  
W25X40BL(SS)@SOIC8 [CX1044]  
W25X40BL-SV8 [CX1045]  
W25X40BV [CX0001]  
W25X40BV(SS)@SOIC8 [CX1044]  
W25X40BV-SV8 [CX1045]  
W25X40CL [CX0001]  
W25X40CL(SS)@SOIC8 [CX1044]  
W25X40CL-SV8 [CX1045]  
W25X40L [CX0001]  
W25X40L(SS)@SOIC8 [CX1044]  
W25X40V [CX0001]  
W25X40V(SS)@SOIC8 [CX1044]  
W25X41CL@SOIC8 [CX1045]  
W25X64@SOIC16(ISP) [CX0001]  
W25X64@SOIC8(ISP) [CX0001]  
W25X64BV(SS)@SOIC8 [CX1044#1]  
W25X64V(SF)@SOIC16 [CX1033#1]  
W25X64V(ZE)@WSON8 [CX4006#1]  
W25X80(SN)@SOIC8 [CX1045]  
W25X80(ZP)@WSON8 [CX4005]  
W25X80AL-SN8 [CX1045]  
W25X80AL-ZP8 [CX4005]  
W25X80AV(SN)@SOIC8 [CX1045]  
W25X80AV(ZP)@WSON8 [CX4005]  
W25X80BL-SN8 [CX1045]  
W25X80BL-ZP8 [CX4005]  
W25X80L(SS)@SOIC8 [CX1044]  
W25X80V [CX0001]  
W25X80V(SS)@SOIC8 [CX1044]  
W27C01 [CX0001]  
W27C01@VSOP32 [CX1003]  
W27C010@PLCC32 [CX2032]  
W27C02 [CX0001]  
W27C02@VSOP32 [CX1003]  
W27C020@PLCC32 [CX2032]  
W27C020M@PLCC32 [CX2032]  
W27C257@PLCC32 [CX2032]  
W27C4096@PLCC44 [CX2044]  
W27C512 [CX0001]  
W27C512@TSOP28 [CX1024]  
W27C520@TSSOP20 [CX1000]  
W27E01@PLCC32 [CX2032]  
W27E010 [CX0001]  
W27E010@SOIC32 [CX1034]  
W27E02@PLCC32 [CX2032]  
W27E020 [CX0001]  
W27E040 [CX0001]  
W27E040@SOIC32 [CX1034]  
W27E257@PLCC32 [CX2032]  
W27E4096 [CX0001]  
W27E4096@TSOP40 [CX1006]  
W27E512@PLCC32 [CX2032]  
W27E520@SOIC20 [CX1033]

W25X40(ZP)@WSON8 [CX4005]  
W25X40AL(SN)@SOIC8 [CX1045]  
W25X40AL(ZP)@WSON8 [CX4005]  
W25X40AV(SN)@SOIC8 [CX1045]  
W25X40AV(ZP)@WSON8 [CX4005]  
W25X40BL(SN)@SOIC8 [CX1045]  
W25X40BL(ZP)@WSON8 [CX4005]  
W25X40BL-UX8 [CX4002]  
W25X40BV(SN)@SOIC8 [CX1045]  
W25X40BV(ZP)@WSON8 [CX4005]  
W25X40BV-UX8 [CX4002]  
W25X40CL(SN)@SOIC8 [CX1045]  
W25X40CL(ZP)@WSON8 [CX4005]  
W25X40CL-UX8 [CX4002]  
W25X40L(SN)@SOIC8 [CX1045]  
W25X40L(ZP)@WSON8 [CX4005]  
W25X40V(SN)@SOIC8 [CX1045]  
W25X40V(ZP)@WSON8 [CX4005]  
W25X64@SOIC16 [CX1033#1]  
W25X64@SOIC8 [CX1044#1]  
W25X64BV(SF)@SOIC16 [CX1033#1]  
W25X64BV(ZE)@WSON8 [CX4006#1]  
W25X64V(SS)@SOIC8 [CX1044#1]  
W25X80 [CX0001]  
W25X80(SS)@SOIC8 [CX1044]  
W25X80AL [CX0001]  
W25X80AL-SS8 [CX1044]  
W25X80AV [CX0001]  
W25X80AV(SS)@SOIC8 [CX1044]  
W25X80BL [CX0001]  
W25X80BL-SS8 [CX1044]  
W25X80L [CX0001]  
W25X80L(ZP)@WSON8 [CX4005]  
W25X80V(SN)@SOIC8 [CX1045]  
W25X80V(ZP)@WSON8 [CX4005]  
W27C01@PLCC32 [CX2032]  
W27C010 [CX0001]  
W27C010@SOIC32 [CX1034]  
W27C02@PLCC32 [CX2032]  
W27C020 [CX0001]  
W27C020M [CX0001]  
W27C257 [CX0001]  
W27C4096 [CX0001]  
W27C4096@TSOP40 [CX1006]  
W27C512@PLCC32 [CX2032]  
W27C520@SOIC20 [CX1033]  
W27E01 [CX0001]  
W27E01@VSOP32 [CX1003]  
W27E010@PLCC32 [CX2032]  
W27E02 [CX0001]  
W27E02@VSOP32 [CX1003]  
W27E020@PLCC32 [CX2032]  
W27E040@PLCC32 [CX2032]  
W27E257 [CX0001]  
W27E400 [CX0001]  
W27E4096@PLCC44 [CX2044]  
W27E512 [CX0001]  
W27E512@TSOP28 [CX1024]  
W27E520@TSSOP20 [CX1000]

W27L01 [CX0001]  
W27L01@VSOP32 [CX1003]  
W27L010@PLCC32 [CX2032]  
W27L02@PLCC32 [CX2032]  
W27L520@SOIC20 [CX1033]  
W28F321BB@FBGA48 [CX5064]  
W28F321TB@FBGA48 [CX5064]  
W28F641BB@FBGA48 [CX5085]  
W28F641TB@FBGA48 [CX5085]  
W28J160BT@TSOP48 [CX1004]  
W28J161BB@TFBGA48 [CX5085]  
W28J320BT@TSOP48 [CX1004]  
W28J321BB@TFBGA48 [CX5085]  
W28J800BT@TSOP48 [CX1004]  
W28V400BT@TSOP48 [CX1004]  
W29C010 [CX0001]  
W29C011A [CX0001]  
W29C020 [CX0001]  
W29C020@SOIC32  
W29C020C [CX0001]  
W29C020C@TSOP32 [CX1002]  
W29C040 [CX0001]  
W29C040@TSOP32 [CX1002]  
W29C101 [CX0001]  
W29C101@TSOP40 [CX1006]  
W29C102@PLCC44 [CX2044]  
W29C102@VSOP40 [CX1005]  
W29EE010@PLCC32 [CX2032]  
W29EE011 [CX0001]  
W29EE011@TSOP32 [CX1002]  
W29EE012@PLCC32 [CX2032]  
W29EE512 [CX0001]  
W29EE512@TSOP32 [CX1002]  
W29F040@PLCC32 [CX2032]  
W29F102P@PLCC44 [CX2044]  
W29GL032CB@FBGA48 [CX5002]  
W29GL032CB@TSOP48 [CX1004]  
W29GL032CH@TSOP56 [CX1011]  
W29GL032CL@TSOP56 [CX1011]  
W29GL032CT@FBGA64 [CX5074]  
W29GL064CB@FBGA48 [CX5002]  
W29GL064CB@TSOP48 [CX1004]  
W29GL064CH@TSOP56 [CX1011]  
W29GL064CL@TSOP56 [CX1011]  
W29GL064CT@FBGA64 [CX5074]  
W29GL128CH@FBGA64 [CX5074]  
W29GL128CL@FBGA64 [CX5074]  
W29L102P@PLCC44 [CX2044]  
W39F010 [CX0001]  
W39F010@TSOP32[12.4mm] [CX1003]  
W39L010@PLCC32 [CX2032]  
W39L020@PLCC32 [CX2032]  
W39L020@TSOP32[18.4mm] [CX1002]  
W39L040@TSOP32[12.4mm] [CX1003]  
W39L040A [CX0001]  
W39L040A@TSOP32 [CX1002]  
W39L512@PLCC32 [CX2032]  
W39V040AP@PLCC32 [CX2032]  
W39V040B(P)@PLCC32 [CX2032]

W27L01@PLCC32 [CX2032]  
W27L010 [CX0001]  
W27L02 [CX0001]  
W27L02@VSOP32 [CX1003]  
W27L520@TSOP20 [CX1000]  
W28F321BT@TSOP48 [CX1004]  
W28F321TT@TSOP48 [CX1004]  
W28F641BT@TSOP48 [CX1004]  
W28F641TT@TSOP48 [CX1004]  
W28J160TT@TSOP48 [CX1004]  
W28J161TB@TFBGA48 [CX5085]  
W28J320TT@TSOP48 [CX1004]  
W28J321TB@TFBGA48 [CX5085]  
W28J800TT@TSOP48 [CX1004]  
W28V400TT@TSOP48 [CX1004]  
W29C010@PLCC32 [CX2032]  
W29C011A@PLCC32 [CX2032]  
W29C020@PLCC32 [CX2032]  
W29C020@TSOP32 [CX1002]  
W29C020C@PLCC32 [CX2032]  
W29C020C@VSOP32 [CX1003]  
W29C040@PLCC32 [CX2032]  
W29C040@VSOP32 [CX1003]  
W29C101@PLCC44 [CX2044]  
W29C102 [CX0001]  
W29C102@TSOP40 [CX1006]  
W29EE010 [CX0001]  
W29EE010@TSOP32 [CX1002]  
W29EE011@PLCC32 [CX2032]  
W29EE012 [CX0001]  
W29EE012@SOIC32 [CX1019]  
W29EE512@PLCC32 [CX2032]  
W29F040 [CX0001]  
W29F040@TSOP32 [CX1002]  
W29F102Q@TSOP40 [CX1005]  
W29GL032CB@FBGA64 [CX5074]  
W29GL032CH@FBGA64 [CX5074]  
W29GL032CL@FBGA64 [CX5074]  
W29GL032CT@FBGA48 [CX5002]  
W29GL032CT@TSOP48 [CX1004]  
W29GL064CB@FBGA64 [CX5074]  
W29GL064CH@FBGA64 [CX5074]  
W29GL064CL@FBGA64 [CX5074]  
W29GL064CT@FBGA48 [CX5002]  
W29GL064CT@TSOP48 [CX1004]  
W29GL128CH@TSOP56 [CX1011]  
W29GL128CL@TSOP56 [CX1011]  
W29L102Q@TSOP40 [CX1005]  
W39F010@PLCC32 [CX2032]  
W39F010@TSOP32[18.4mm] [CX1002]  
W39L010@TSOP32 [CX1003]  
W39L020@TSOP32[12.4mm] [CX1003]  
W39L040@PLCC32 [CX2032]  
W39L040@TSOP32[18.4mm] [CX1002]  
W39L040A@PLCC32 [CX2032]  
W39L040A@VSOP32 [CX1003]  
W39L512@TSOP32 [CX1003]  
W39V040AQ@VSOP32 [CX1003]  
W39V040B(Q)@VSOP32 [CX1003]

W39V040CP@PLCC32 [CX2032]  
W39V040CQ@VSOP32 [CX1003]  
W39V040FAP@PLCC32 [CX2032]  
W39V040FAT@TSOP40 [CX1006]  
W39V040FB(Q)@VSOP32 [CX1003]  
W39V040FCPZ@PLCC32 [CX2032]  
W39V040FCQZ@VSOP32 [CX1003]  
W39V080A(Q)@VSOP32 [CX1003]  
W39V080FA(P)@PLCC32 [CX2032]  
W39V080FA(T)@TSOP40 [CX1006]  
W45B012@SON8 [CX4005]  
W45B512@SON8 [CX4005]  
W49F002@PLCC32 [CX2032]  
W49F002B [CX0001]  
W49F002B@TSOP32 [CX1002]  
W49F002N@PLCC32 [CX2032]  
W49F002U [CX0001]  
W49F002U@TSOP32 [CX1002]  
W49F020@PLCC32 [CX2032]  
W49F102P@PLCC44 [CX2044]  
W49F201S@PSOP44 [CX1014]  
W49L102P@PLCC44 [CX2044]  
W49L201S@PSOP44 [CX1014]  
W49L401S@PSOP44 [CX1014]  
W49V002A@PLCC32 [CX2032]  
W49V002FA@PLCC32 [CX2032]  
W49V002FP@PLCC32 [CX2032]  
W49V002P@PLCC32 [CX2032]  
W55F05 [CX0001]  
W55F20 [CX0001]

W39V040CPZ@PLCC32 [CX2032]  
W39V040CQZ@VSOP32 [CX1003]  
W39V040FAQ@VSOP32 [CX1003]  
W39V040FB(P)@PLCC32 [CX2032]  
W39V040FCP@PLCC32 [CX2032]  
W39V040FCQ@VSOP32 [CX1003]  
W39V080A(P)@PLCC32 [CX2032]  
W39V080A(T)@TSOP40 [CX1006]  
W39V080FA(Q)@VSOP32 [CX1003]  
W45B012@PLCC32 [CX2032]  
W45B512@PLCC32 [CX2032]  
W49F002 [CX0001]  
W49F002@TSOP32 [CX1002]  
W49F002B@PLCC32 [CX2032]  
W49F002N [CX0001]  
W49F002N@TSOP32 [CX1002]  
W49F002U@PLCC32 [CX2032]  
W49F020 [CX0001]  
W49F020@TSOP32 [CX1002]  
W49F102Q@TSOP40 [CX1005]  
W49F201T@TSOP48 [CX1004]  
W49L102Q@TSOP40 [CX1005]  
W49L201T@TSOP48 [CX1004]  
W49L401T@TSOP48 [CX1004]  
W49V002A@VSOP32 [CX1003]  
W49V002FA@VSOP32 [CX1003]  
W49V002FP@VSOP32 [CX1003]  
W49V002P@VSOP32 [CX1003]  
W55F10A [CX0001]

## MICROCONTROLLER

N79E342AKG [CX0001]  
N79E342RAKG [CX0001]  
N79E352AEG [CX0001]  
N79E352ALG@TQFP48 [CX3007]  
N79E8213AKG [CX0001]  
N79E8213RAKG [CX0001]  
W77E058A [CX0001]  
W77E058A@TQFP44 [CX3002]  
W77E516@PLCC44 [CX2044]  
W77E532 [CX0001]  
W77E532@TQFP44 [CX3002]  
W77E532A@PLCC44 [CX2044]  
W77E58 [CX0001]  
W77E58@TQFP44 [CX3002]  
W77IE58@PLCC44 [CX2044]  
W77L058A [CX0001]  
W77L058A@TQFP44 [CX3002]  
W77L516A@PLCC44 [CX2044]  
W77L532A [CX0001]  
W77L532A@TQFP44 [CX3002]  
W77LE516@PLCC44 [CX2044]  
W77LE532 [CX0001]  
W77LE532@TQFP44 [CX3002]  
W77LE58@PLCC44 [CX2044]  
W77LE58A [CX0001]  
W77LE58A@TQFP44 [CX3002]

N79E342ASG@SOP16 [CX1033]  
N79E342RASG@SOP16 [CX1033]  
N79E352AFG@TQFP44 [CX3002]  
N79E352APG@PLCC44 [CX2044]  
N79E8213ASG@SOP20 [CX1033]  
N79E8213RASG@SOP20 [CX1033]  
W77E058A@PLCC44 [CX2044]  
W77E516 [CX0001]  
W77E516@TQFP44 [CX3002]  
W77E532@PLCC44 [CX2044]  
W77E532A [CX0001]  
W77E532A@TQFP44 [CX3002]  
W77E58@PLCC44 [CX2044]  
W77IE58 [CX0001]  
W77IE58@TQFP44 [CX3002]  
W77L058A@PLCC44 [CX2044]  
W77L516A [CX0001]  
W77L516A@TQFP44 [CX3002]  
W77L532A@PLCC44 [CX2044]  
W77LE516 [CX0001]  
W77LE516@TQFP44 [CX3002]  
W77LE532@PLCC44 [CX2044]  
W77LE58 [CX0001]  
W77LE58@TQFP44 [CX3002]  
W77LE58A@PLCC44 [CX2044]  
W78E051B [CX0001]

W78E051B@PLCC44 [CX2044]  
W78E051C [CX0001]  
W78E051C@TQFP44 [CX3002]  
W78E051DFG@PQFP44 [CX3002]  
W78E051DPG@PLCC44 [CX2044]  
W78E052B@PLCC44 [CX2044]  
W78E052C [CX0001]  
W78E052C@TQFP44 [CX3002]  
W78E052DFG@PQFP44 [CX3002]  
W78E052DPG@PLCC44 [CX2044]  
W78E054B@PLCC44 [CX2044]  
W78E054C [CX0001]  
W78E054C@TQFP44 [CX3002]  
W78E054DFG@PQFP44 [CX3002]  
W78E054DPG@PLCC44 [CX2044]  
W78E058B@PLCC44 [CX2044]  
W78E058DDG [CX0001]  
W78E058DLG@TQFP48 [CX3007]  
W78E065 [CX0001]  
W78E065@TQFP44 [CX3002]  
W78E354(dip48) [CX0001]  
W78E365 [CX0001]  
W78E365@TQFP44 [CX3002]  
W78E365A@PLCC44 [CX2044]  
W78E374B [CX0001]  
W78E378E [CX0001]  
W78E51 [CX0001]  
W78E51@TQFP44 [CX3002]  
W78E516@PLCC44 [CX2044]  
W78E516B [CX0001]  
W78E516B@TQFP44 [CX3002]  
W78E516DFG@TQFP44 [CX3002]  
W78E516DPG@PLCC44 [CX2044]  
W78E51B@PLCC44 [CX2044]  
W78E51B@TQFP44 [CX3003]  
W78E51C@PLCC44 [CX2044]  
W78E52 [CX0001]  
W78E52@TQFP44 [CX3002]  
W78E52B@PLCC44 [CX2044]  
W78E52C [CX0001]  
W78E52C@TQFP44 [CX3002]  
W78E54@PLCC44 [CX2044]  
W78E54@TQFP44 [CX3003]  
W78E54B@PLCC44 [CX2044]  
W78E54C [CX0001]  
W78E54C@TQFP44 [CX3002]  
W78E58@PLCC44 [CX2044]  
W78E58@TQFP44 [CX3003]  
W78E58B@PLCC44 [CX2044]  
W78E62B [CX0001]  
W78E62B@TQFP44 [CX3002]  
W78E65@PLCC44 [CX2044]  
W78E858 [CX0001]  
W78E858@TQFP44 [CX3002]  
W78ERD2@PLCC44 [CX2044]  
W78I051DDG [CX0001]  
W78I051DLG@LQFP48 [CX3007]  
W78I052 [CX0001]  
W78I052DDG [CX0001]

W78E051B@TQFP44 [CX3002]  
W78E051C@PLCC44 [CX2044]  
W78E051DDG [CX0001]  
W78E051DLG@LQFP48 [CX3007]  
W78E052B [CX0001]  
W78E052B@TQFP44 [CX3002]  
W78E052C@PLCC44 [CX2044]  
W78E052DDG [CX0001]  
W78E052DLG@LQFP48 [CX3007]  
W78E054B [CX0001]  
W78E054B@TQFP44 [CX3002]  
W78E054C@PLCC44 [CX2044]  
W78E054DDG [CX0001]  
W78E054DLG@LQFP48 [CX3007]  
W78E058B [CX0001]  
W78E058B@TQFP44 [CX3002]  
W78E058DFG@TQFP44 [CX3002]  
W78E058DPG@PLCC44 [CX2044]  
W78E065@PLCC44 [CX2044]  
W78E354(dip40) [CX0001]  
W78E354@PLCC68 [CX2068]  
W78E365@PLCC44 [CX2044]  
W78E365A [CX0001]  
W78E365A@TQFP44 [CX3002]  
W78E378 [CX0001]  
W78E378P@PLCC44 [CX2044]  
W78E51@PLCC44 [CX2044]  
W78E516 [CX0001]  
W78E516@TQFP44 [CX3002]  
W78E516B@PLCC44 [CX2044]  
W78E516DDG [CX0001]  
W78E516DLG@TQFP48 [CX3007]  
W78E51B [CX0001]  
W78E51B@PQFP44 [CX3002]  
W78E51C [CX0001]  
W78E51C@TQFP44 [CX3002]  
W78E52@PLCC44 [CX2044]  
W78E52B [CX0001]  
W78E52B@TQFP44 [CX3002]  
W78E52C@PLCC44 [CX2044]  
W78E54 [CX0001]  
W78E54@PQFP44 [CX3002]  
W78E54B [CX0001]  
W78E54B@TQFP44 [CX3002]  
W78E54C@PLCC44 [CX2044]  
W78E58 [CX0001]  
W78E58@PQFP44 [CX3002]  
W78E58B [CX0001]  
W78E58B@TQFP44 [CX3002]  
W78E62B@PLCC44 [CX2044]  
W78E65 [CX0001]  
W78E65@TQFP44 [CX3002]  
W78E858@PLCC44 [CX2044]  
W78ERD2 [CX0001]  
W78ERD2@TQFP44 [CX3002]  
W78I051DFG@PQFP44 [CX3002]  
W78I051DPG@PLCC44 [CX2044]  
W78I052@PLCC44 [CX2044]  
W78I052DFG@PQFP44 [CX3002]

W78I052DLG@LQFP48 [CX3007]  
W78I054 [CX0001]  
W78I054DDG [CX0001]  
W78I054DLG@LQFP48 [CX3007]  
W78IE52 [CX0001]  
W78IE54 [CX0001]  
W78IRD2 [CX0001]  
W78IRD2@TQFP44 [CX3002]  
W78L051A@PLCC44 [CX2044]  
W78L051C [CX0001]  
W78L051C@TQFP44 [CX3002]  
W78L052A@PLCC44 [CX2044]  
W78L052C [CX0001]  
W78L052C@TQFP44 [CX3002]  
W78L054A@PLCC44 [CX2044]  
W78L054C [CX0001]  
W78L054C@TQFP44 [CX3002]  
W78L058A@PLCC44 [CX2044]  
W78L365 [CX0001]  
W78L365@TQFP44 [CX3002]  
W78L365A [CX0001]  
W78L365A@TQFP44 [CX3002]  
W78L516 [CX0001]  
W78L516@TQFP44 [CX3002]  
W78L516A@PLCC44 [CX2044]  
W78L812A [CX0001]  
W78L812A@TQFP44 [CX3002]  
W78LE365@PLCC44 [CX2044]  
W78LE365@TQFP48 [CX3007]  
W78LE51@PLCC44 [CX2044]  
W78LE516 [CX0001]  
W78LE516@TQFP44 [CX3002]  
W78LE51C@PLCC44 [CX2044]  
W78LE52 [CX0001]  
W78LE52@TQFP44 [CX3002]  
W78LE52C@PLCC44 [CX2044]  
W78LE54 [CX0001]  
W78LE54@TQFP44 [CX3002]  
W78LE54C@PLCC44 [CX2044]  
W78LE58 [CX0001]  
W78LE58@TQFP44 [CX3002]  
W78LE812@PLCC44 [CX2044]  
W79E201@PLCC44 [CX2044]  
W79E2051(dip14) [CX0001]  
W79E2051(dip20) [CX0001]  
W79E2051@SOIC16 [CX1033]  
W79E2051R(dip20) [CX0001]  
W79E225ALG@TQFP48 [CX3007]  
W79E226ALG@TQFP48 [CX3007]  
W79E227ALG@TQFP48 [CX3007]  
W79E4051(dip14) [CX0001]  
W79E4051(dip20) [CX0001]  
W79E4051@SOIC16 [CX1033]  
W79E4051R(dip20) [CX0001]  
W79E532 [CX0001]  
W79E532@TQFP44 [CX3002]  
W79E532A@PLCC44 [CX2044]  
W79E533A@PLCC44 [CX2044]  
W79E632@PLCC44 [CX2044]

W78I052DPG@PLCC44 [CX2044]  
W78I054@PLCC44 [CX2044]  
W78I054DFG@PQFP44 [CX3002]  
W78I054DPG@PLCC44 [CX2044]  
W78IE52@PLCC44 [CX2044]  
W78IE54@PLCC44 [CX2044]  
W78IRD2@PLCC44 [CX2044]  
W78L051A [CX0001]  
W78L051A@TQFP44 [CX3002]  
W78L051C@PLCC44 [CX2044]  
W78L052A [CX0001]  
W78L052A@TQFP44 [CX3002]  
W78L052C@PLCC44 [CX2044]  
W78L054A [CX0001]  
W78L054A@TQFP44 [CX3002]  
W78L054C@PLCC44 [CX2044]  
W78L058A [CX0001]  
W78L058A@TQFP44 [CX3002]  
W78L365@PLCC44 [CX2044]  
W78L365@TQFP48 [CX3007]  
W78L365A@PLCC44 [CX2044]  
W78L365A@TQFP48 [CX3007]  
W78L516@PLCC44 [CX2044]  
W78L516A [CX0001]  
W78L516A@TQFP44 [CX3002]  
W78L812A@PLCC44 [CX2044]  
W78LE365 [CX0001]  
W78LE365@TQFP44 [CX3002]  
W78LE51 [CX0001]  
W78LE51@TQFP44 [CX3002]  
W78LE516@PLCC44 [CX2044]  
W78LE51C [CX0001]  
W78LE51C@TQFP44 [CX3002]  
W78LE52@PLCC44 [CX2044]  
W78LE52C [CX0001]  
W78LE52C@TQFP44 [CX3002]  
W78LE54@PLCC44 [CX2044]  
W78LE54C [CX0001]  
W78LE54C@TQFP44 [CX3002]  
W78LE58@PLCC44 [CX2044]  
W78LE812 [CX0001]  
W78LE812@TQFP44 [CX3002]  
W79E201@TQFP44 [CX3002]  
W79E2051(dip16) [CX0001]  
W79E2051@SOIC14 [CX1033]  
W79E2051@SOIC20 [CX1033]  
W79E2051R@SOIC20 [CX1033]  
W79E225APG@PLCC44 [CX2044]  
W79E226APG@PLCC44 [CX2044]  
W79E227APG@PLCC44 [CX2044]  
W79E4051(dip16) [CX0001]  
W79E4051@SOIC14 [CX1033]  
W79E4051@SOIC20 [CX1033]  
W79E4051R@SOIC20 [CX1033]  
W79E532@PLCC44 [CX2044]  
W79E532A [CX0001]  
W79E532A@TQFP44 [CX3002]  
W79E632 [CX0001]  
W79E632@TQFP44 [CX3002]



W79E632A [CX0001]  
W79E632A@TQFP44 [CX3002]  
W79E801A [CX0001]  
W79E802A [CX0001]  
W79E803A [CX0001]  
W79E804A [CX0001]  
W79E821A [CX0001]  
W79E822A [CX0001]  
W79E822B [CX0001]  
W79E823A [CX0001]  
W79E823B [CX0001]  
W79E824A [CX0001]  
W79E825A [CX0001]  
W79E831A [CX0001]  
W79E832A [CX0001]  
W79E833A [CX0001]  
W79E834A [CX0001]  
W79L532 [CX0001]  
W79L532@TQFP44 [CX3002]  
W79L632@PLCC44 [CX2044]  
W79L632A [CX0001]  
W79L632A@TQFP44 [CX3002]  
W99100DG@TQFP48 [CX3007]

W79E632A@PLCC44 [CX2044]  
W79E633A@PLCC44 [CX2044]  
W79E801A@SOIC20 [CX1033]  
W79E802A@SOIC20 [CX1033]  
W79E803A@SOIC20 [CX1033]  
W79E804A@SOIC20 [CX1033]  
W79E821A@SOIC20 [CX1033]  
W79E822A@SOIC20 [CX1033]  
W79E822B@SOIC20 [CX1033]  
W79E823A@SOIC20 [CX1033]  
W79E823B@SOIC20 [CX1033]  
W79E824A@SOIC20 [CX1033]  
W79E825A@SOIC20 [CX1033]  
W79E831A@SOIC28 [CX1033]  
W79E832A@SOIC28 [CX1033]  
W79E833A@SOIC28 [CX1033]  
W79E834A@SOIC28 [CX1033]  
W79L532@PLCC44 [CX2044]  
W79L632 [CX0001]  
W79L632@TQFP44 [CX3002]  
W79L632A@PLCC44 [CX2044]  
W79L633A@PLCC44 [CX2044]

## WING Shing

### E (E) PROM/FRAM/NVRAM

WS24C02 [CX0001]  
WS24C04 [CX0001]  
WS24C08 [CX0001]  
WS24C16 [CX0001]  
WS24W04 [CX0001]  
WS24W08 [CX0001]  
WS24W16 [CX0001]  
WS24C02@SOP8 [CX1045]  
WS24C04@SOP8 [CX1045]  
WS24C08@SOP8 [CX1045]  
WS24C16@SOP8 [CX1045]  
WS24W04@SOP8 [CX1045]  
WS24W08@SOP8 [CX1045]  
WS24W16@SOP8 [CX1045]

## WSI

### E (E) PROM/FRAM/NVRAM

WS27C010L [CX0001]  
WS27C010L@TSOP32 [CX1002]  
WS27C010R@PLCC32 [CX2032]  
WS27C040L [CX0001]  
WS27C040L@TSOP32 [CX1002]  
WS27C128F@PLCC32 [CX2032]  
WS27C128L@PLCC32 [CX2032]  
WS27C210L@PLCC44 [CX2044]  
WS27C256F@PLCC32 [CX2032]  
WS27C256L@PLCC32 [CX2032]  
WS27C512F@PLCC32 [CX2032]  
WS27C512L@PLCC32 [CX2032]  
WS27C64@PLCC32 [CX2032]  
WS27C64F@PLCC32 [CX2032]  
WS27C64L@PLCC32 [CX2032]  
WS57C128@PLCC32 [CX2032]  
WS57C128F@PLCC32 [CX2032]  
WS27C010L@PLCC32 [CX2032]  
WS27C010R [CX0001]  
WS27C010R@TSOP32 [CX1002]  
WS27C040L@PLCC32 [CX2032]  
WS27C128F [CX0001]  
WS27C128L [CX0001]  
WS27C210L [CX0001]  
WS27C256F [CX0001]  
WS27C256L [CX0001]  
WS27C512F [CX0001]  
WS27C512L [CX0001]  
WS27C64 [CX0001]  
WS27C64F [CX0001]  
WS27C64L [CX0001]  
WS57C128 [CX0001]  
WS57C128F [CX0001]  
WS57C128FB [CX0001]

WS57C128FB@PLCC32 [CX2032]  
WS57C191@PLCC28 [CX2028]  
WS57C191B@PLCC28 [CX2028]  
WS57C191C@PLCC28 [CX2028]  
WS57C256F@PLCC32 [CX2032]  
WS57C256FB@PLCC32 [CX2032]  
WS57C257@PLCC44 [CX2044]  
WS57C291@PLCC28 [CX2028]  
WS57C291B@PLCC28 [CX2028]  
WS57C291C@PLCC28 [CX2028]  
WS57C43@PLCC28 [CX2028]  
WS57C43B@PLCC28 [CX2028]  
WS57C43C@PLCC28 [CX2028]  
WS57C45@PLCC28 [CX2028]  
WS57C49@PLCC28 [CX2028]  
WS57C49B@PLCC28 [CX2028]  
WS57C49C@PLCC28 [CX2028]  
WS57C51@PLCC32 [CX2032]  
WS57C51B@PLCC32 [CX2032]  
WS57C51C@PLCC32 [CX2032]  
WS57C64F@PLCC32 [CX2032]  
WS57C71C@PLCC32 [CX2032]  
WS57LV191C@PLCC28 [CX2028]  
WS57LV291C@PLCC28 [CX2028]

WS57C191 [CX0001]  
WS57C191B [CX0001]  
WS57C191C [CX0001]  
WS57C256F [CX0001]  
WS57C256FB [CX0001]  
WS57C257 [CX0001]  
WS57C291 [CX0001]  
WS57C291B [CX0001]  
WS57C291C [CX0001]  
WS57C43 [CX0001]  
WS57C43B [CX0001]  
WS57C43C [CX0001]  
WS57C45 [CX0001]  
WS57C49 [CX0001]  
WS57C49B [CX0001]  
WS57C49C [CX0001]  
WS57C51 [CX0001]  
WS57C51B [CX0001]  
WS57C51C [CX0001]  
WS57C64F [CX0001]  
WS57C71C [CX0001]  
WS57LV191C [CX0001]  
WS57LV291C [CX0001]

## MICROCONTROLLER

PSD211R@PLCC44 [CX2044]  
PSD301@PLCC44 [CX2044]  
PSD301B@PLCC44 [CX2044]  
PSD301L@PLCC44 [CX2044]  
PSD301R@PLCC44 [CX2044]  
PSD301RV@PLCC44 [CX2044]  
PSD302@PLCC44 [CX2044]  
PSD302B@PLCC44 [CX2044]  
PSD302C1@PLCC44 [CX2044]  
PSD302L@TQFP44 [CX3003]  
PSD302R@TQFP44 [CX3003]  
PSD302V@PLCC44 [CX2044]  
PSD303@TQFP44 [CX3003]  
PSD303L@PLCC44 [CX2044]  
PSD303R@PLCC44 [CX2044]  
PSD303RV@PLCC44 [CX2044]  
PSD311@PLCC44 [CX2044]  
PSD311B@PLCC44 [CX2044]  
PSD311L@PLCC44 [CX2044]  
PSD311R@PLCC44 [CX2044]  
PSD311RV@PLCC44 [CX2044]  
PSD312@PLCC44 [CX2044]  
PSD312B@PLCC44 [CX2044]  
PSD312L@PLCC44 [CX2044]  
PSD312R@PLCC44 [CX2044]  
PSD312RV@PLCC44 [CX2044]  
PSD313@PLCC44 [CX2044]  
PSD313-B@PLCC44 [CX2044]  
PSD313C1@PLCC44 [CX2044]  
PSD313L@TQFP44 [CX3003]  
PSD313R@TQFP44 [CX3003]  
PSD313V@PLCC44 [CX2044]

PSD211R@TQFP44 [CX3003]  
PSD301@TQFP44 [CX3003]  
PSD301C1@PLCC44 [CX2044]  
PSD301L@TQFP44 [CX3003]  
PSD301R@TQFP44 [CX3003]  
PSD301V@PLCC44 [CX2044]  
PSD302@TQFP44 [CX3003]  
PSD302B@PLCC44(USA) [CX2044]  
PSD302L@PLCC44 [CX2044]  
PSD302R@PLCC44 [CX2044]  
PSD302RV@PLCC44 [CX2044]  
PSD303@PLCC44 [CX2044]  
PSD303C1@PLCC44 [CX2044]  
PSD303L@TQFP44 [CX3003]  
PSD303R@TQFP44 [CX3003]  
PSD303V@PLCC44 [CX2044]  
PSD311@TQFP44 [CX3003]  
PSD311C1@PLCC44 [CX2044]  
PSD311L@TQFP44 [CX3003]  
PSD311R@TQFP44 [CX3003]  
PSD311V@PLCC44 [CX2044]  
PSD312@TQFP44 [CX3046]  
PSD312C1@PLCC44 [CX2044]  
PSD312L@TQFP44 [CX3046]  
PSD312R@TQFP44 [CX3046]  
PSD312V@PLCC44 [CX2044]  
PSD313@TQFP44 [CX3003]  
PSD313-B@TQFP44 [CX3003]  
PSD313L@PLCC44 [CX2044]  
PSD313R@PLCC44 [CX2044]  
PSD313RV@PLCC44 [CX2044]  
ZPSD211R@PLCC44 [CX2044]

ZPSD211R@TQFP44 [CX3003]  
ZPSD211RV@TQFP44 [CX3003]  
ZPSD301@TQFP44 [CX3003]  
ZPSD301L@TQFP44 [CX3003]  
ZPSD301R@TQFP44 [CX3003]  
ZPSD301RL@TQFP44 [CX3003]  
ZPSD301RV@TQFP44 [CX3003]  
ZPSD301V@TQFP44 [CX3003]  
ZPSD302@TQFP44 [CX3003]  
ZPSD302B@PLCC44(USA) [CX2044]  
ZPSD302L@TQFP44 [CX3003]  
ZPSD302R@TQFP44 [CX3003]  
ZPSD302RL@TQFP44 [CX3003]  
ZPSD302RV@TQFP44 [CX3003]  
ZPSD302V@TQFP44 [CX3003]  
ZPSD303@TQFP44 [CX3003]  
ZPSD303L@TQFP44 [CX3003]  
ZPSD303R@TQFP44 [CX3003]  
ZPSD303RL@TQFP44 [CX3003]  
ZPSD303RV@TQFP44 [CX3003]  
ZPSD303V@TQFP44 [CX3003]  
ZPSD311@TQFP44 [CX3003]  
ZPSD311L@TQFP44 [CX3003]  
ZPSD311R@TQFP44 [CX3003]  
ZPSD311RL@TQFP44 [CX3003]  
ZPSD311RV@TQFP44 [CX3003]  
ZPSD311V@TQFP44 [CX3003]  
ZPSD312@TQFP44 [CX3046]  
ZPSD312L@PLCC44 [CX2044]  
ZPSD312R@PLCC44 [CX2044]  
ZPSD312RL@PLCC44 [CX2044]  
ZPSD312RV@PLCC44 [CX2044]  
ZPSD312V@PLCC44 [CX2044]  
ZPSD313@PLCC44 [CX2044]  
ZPSD313L@PLCC44 [CX2044]  
ZPSD313R@PLCC44 [CX2044]  
ZPSD313RL@PLCC44 [CX2044]  
ZPSD313RV@PLCC44 [CX2044]  
ZPSD313V@PLCC44 [CX2044]

ZPSD211RV@PLCC44 [CX2044]  
ZPSD301@PLCC44 [CX2044]  
ZPSD301L@PLCC44 [CX2044]  
ZPSD301R@PLCC44 [CX2044]  
ZPSD301RL@PLCC44 [CX2044]  
ZPSD301RV@PLCC44 [CX2044]  
ZPSD301V@PLCC44 [CX2044]  
ZPSD302@PLCC44 [CX2044]  
ZPSD302B@PLCC44 [CX2044]  
ZPSD302L@PLCC44 [CX2044]  
ZPSD302R@PLCC44 [CX2044]  
ZPSD302RL@PLCC44 [CX2044]  
ZPSD302RV@PLCC44 [CX2044]  
ZPSD302V@PLCC44 [CX2044]  
ZPSD303@PLCC44 [CX2044]  
ZPSD303L@PLCC44 [CX2044]  
ZPSD303R@PLCC44 [CX2044]  
ZPSD303RL@PLCC44 [CX2044]  
ZPSD303RV@PLCC44 [CX2044]  
ZPSD303V@PLCC44 [CX2044]  
ZPSD311@PLCC44 [CX2044]  
ZPSD311L@PLCC44 [CX2044]  
ZPSD311R@PLCC44 [CX2044]  
ZPSD311RL@PLCC44 [CX2044]  
ZPSD311RV@PLCC44 [CX2044]  
ZPSD311V@PLCC44 [CX2044]  
ZPSD312@PLCC44 [CX2044]  
ZPSD312B@PLCC44 [CX2044]  
ZPSD312L@TQFP44 [CX3046]  
ZPSD312R@TQFP44 [CX3046]  
ZPSD312RL@TQFP44 [CX3046]  
ZPSD312RV@TQFP44 [CX3046]  
ZPSD312V@TQFP44 [CX3046]  
ZPSD313@TQFP44 [CX3003]  
ZPSD313L@TQFP44 [CX3003]  
ZPSD313R@TQFP44 [CX3003]  
ZPSD313RL@TQFP44 [CX3003]  
ZPSD313RV@TQFP44 [CX3003]  
ZPSD313V@TQFP44 [CX3003]

## XELTEK

### E (E) PROM / FRAM / NVRAM

EN29GL128H@TSOP56 [CX0001]  
M29F160FT@TSOP48 [CX0001]

M29F160FB@TSOP48 [CX0001]  
X29GL128P90TFIR1@TSOP56 [CX0001]

### MICROCONTROLLER

#####111111111111TST  
#####333333333333MCU  
SP5KTEST-LOG  
ST7FLI49MK1T6 [CX3001]  
ST7FLITE49@QFP32 [CX3001]

#####222222222222UP  
#####444444444444ADT  
ST7FLI49MK1B6 [CX0032]  
ST7FLITE49 [CX0032]  
SYSTEM-CLK-TEST [CX0001]

## XICOR

## E (E) PROM/FRAM/NVRAM

X2004 [CX0001]	X2004@PLCC32 [CX2032]
X2004D [CX0001]	X2004D@PLCC32 [CX2032]
X2004I [CX0001]	X2004I@PLCC32 [CX2032]
X2210 [CX0001]	X2210@SOIC16 [CX1033]
X2210A [CX0001]	X2210A@SOIC16 [CX1033]
X2210I [CX0001]	X2210I@SOIC16 [CX1033]
X2212 [CX0001]	X2212@SOIC20 [CX1033]
X2212A [CX0001]	X2212A@SOIC20 [CX1033]
X2212I [CX0001]	X2212I@SOIC20 [CX1033]
X22C10 [CX0001]	X22C10@SOIC16 [CX1033]
X22C10I [CX0001]	X22C10I@SOIC16 [CX1033]
X22C12 [CX0001]	X22C12@SOIC20 [CX1033]
X22C12I [CX0001]	X22C12I@SOIC20 [CX1033]
X24012 [CX0001]	X24012@SOIC8 [CX1045]
X24022 [CX0001]	X24022@SOIC8 [CX1045]
X24026 [CX0001]	X24026@SOIC8 [CX1045]
X24042 [CX0001]	X24042@SOIC8 [CX1045]
X24164 [CX0001]	X24164@SOIC8 [CX1045]
X24165 [CX0001]	X24165@SOIC8 [CX1045]
X24325 [CX0001]	X24325@SOIC8 [CX1045]
X2444 [CX0001]	X2444I [CX0001]
X24645 [CX0001]	X24645@SOIC8 [CX1045]
X24C00 [CX0001]	X24C00@MSOP8 [CX1059]
X24C00@SOIC8 [CX1045]	X24C01 [CX0001]
X24C01@MSOP8 [CX1015]	X24C01@SOIC8 [CX1045]
X24C01A [CX0001]	X24C01A@SOIC8 [CX1045]
X24C01I [CX0001]	X24C01I@SOIC8 [CX1045]
X24C02 [CX0001]	X24C02@SOIC8 [CX1045]
X24C02I [CX0001]	X24C02I@SOIC8 [CX1045]
X24C04 [CX0001]	X24C04@SOIC14 [CX1030]
X24C04@SOIC8 [CX1045]	X24C04I [CX0001]
X24C04I@SOIC14 [CX1030]	X24C04I@SOIC8 [CX1045]
X24C08 [CX0001]	X24C08@SOIC14 [CX1030]
X24C08@SOIC8 [CX1045]	X24C08I [CX0001]
X24C08I@SOIC14 [CX1030]	X24C08I@SOIC8 [CX1045]
X24C16 [CX0001]	X24C16@SOIC14 [CX1030]
X24C16@SOIC8 [CX1045]	X24C16I [CX0001]
X24C16I@SOIC14 [CX1030]	X24C16I@SOIC8 [CX1045]
X24C44 [CX0001]	X24C44@SOIC8 [CX1045]
X24C44I [CX0001]	X24C44I@SOIC8 [CX1045]
X24C45 [CX0001]	X24C45@SOIC8 [CX1045]
X24C45I [CX0001]	X24C45I@SOIC8 [CX1045]
X24F008(3V) [CX0001]	X24F008(3V)@SOIC8 [CX1045]
X24F008(3V)@TSSOP14 [CX1016]	X24F008(5V) [CX0001]
X24F008(5V)@SOIC8 [CX1045]	X24F008(5V)@TSSOP14 [CX1016]
X24F016(3V) [CX0001]	X24F016(3V)@SOIC8 [CX1045]
X24F016(3V)@TSSOP14 [CX1016]	X24F016(5V) [CX0001]
X24F016(5V)@SOIC8 [CX1045]	X24F016(5V)@TSSOP14 [CX1016]
X24F032(3V) [CX0001]	X24F032(3V)@SOIC8 [CX1045]
X24F032(3V)@TSSOP14 [CX1016]	X24F032(5V) [CX0001]
X24F032(5V)@SOIC8 [CX1045]	X24F032(5V)@TSSOP14 [CX1016]
X24F064(3V) [CX0001]	X24F064(3V)@SOIC8 [CX1045]
X24F064(3V)@TSSOP20 [CX1033]	X24F064(5V) [CX0001]
X24F064(5V)@SOIC8 [CX1045]	X24F064(5V)@TSSOP20 [CX1033]
X25020 [CX0001]	X25020@SOIC8 [CX1045]
X25021 [CX0001]	X25021@SOIC8 [CX1045]
X25040 [CX0001]	X25040@SOIC8 [CX1045]

X25041 [CX0001]  
X25043 [CX0001]  
X25043@SOIC8 [CX1045]  
X25045 [CX0001]  
X25045@SOIC8 [CX1045]  
X25057@MSOP8 [CX1015]  
X25080 [CX0001]  
X25080@TSSOP14 [CX1000]  
X25097@SOIC8 [CX1045]  
X25128 [CX0001]  
X25138 [CX0001]  
X25138@SOIC16 [CX1016]  
X25138@TSSOP8 [CX1059]  
X25160@SOIC8 [CX1045]  
X25163 [CX0001]  
X25163@TSSOP14 [CX1000]  
X25164@SOIC8 [CX1045]  
X25165 [CX0001]  
X25165@TSSOP14 [CX1000]  
X25166@SOIC8 [CX1045]  
X25168 [CX0001]  
X25168@TSSOP14 [CX1000]  
X25169@SOIC8 [CX1045]  
X25170@SOIC8 [CX1045]  
X25256@SOIC8 [CX1045]  
X25320 [CX0001]  
X25323@SOIC8 [CX1045]  
X25324@SOIC8 [CX1045]  
X25325@SOIC8 [CX1045]  
X25326@SOIC8 [CX1045]  
X25328@TSSOP14 [CX1000]  
X25329@TSSOP14 [CX1000]  
X25330@TSSOP14 [CX1000]  
X25401@SOIC8 [CX1045]  
X25640@SOIC14 [CX1016]  
X25642@SOIC14 [CX1016]  
X25642@TSSOP20 [CX1000]  
X25644@SOIC14 [CX1016]  
X25648@SOIC14 [CX1016]  
X25650 [CX0001]  
X25650@SOIC8 [CX1045]  
X25C02 [CX0001]  
X25C02@TSSOP8 [CX1059]  
X25F008(3V)@SOIC8 [CX1045]  
X25F008(3V)@TSSOP20 [CX1033]  
X25F008(5V)@SOIC8 [CX1045]  
X25F008(5V)@TSSOP20 [CX1033]  
X25F016(3V)@SOIC8 [CX1045]  
X25F016(3V)@TSSOP20 [CX1033]  
X25F016(5V)@SOIC8 [CX1045]  
X25F016(5V)@TSSOP20 [CX1033]  
X25F032(3V)@SOIC8 [CX1045]  
X25F032(3V)@TSSOP20 [CX1033]  
X25F032(5V)@SOIC8 [CX1045]  
X25F032(5V)@TSSOP20 [CX1033]  
X25F047(3V)@MSOP8 [CX1015]  
X25F047(3V)@TSSOP8 [CX1000]  
X25F047(5V)@MSOP8 [CX1015]  
X25F047(5V)@TSSOP8 [CX1000]  
X25041@SOIC8 [CX1045]  
X25043@MSOP8 [CX1015]  
X25043@TSSOP14 [CX1000]  
X25045@MSOP8 [CX1015]  
X25045@TSSOP14 [CX1000]  
X25057@TSSOP8 [CX1059]  
X25080@SOIC8 [CX1045]  
X25097@MSOP8 [CX1015]  
X25097@TSSOP8 [CX1059]  
X25128@SOIC16 [CX1016]  
X25138@SOIC14 [CX1016]  
X25138@SOIC8 [CX1045]  
X25160 [CX0001]  
X25160@TSSOP14 [CX1000]  
X25163@SOIC8 [CX1045]  
X25164 [CX0001]  
X25164@TSSOP14 [CX1000]  
X25165@SOIC8 [CX1045]  
X25166 [CX0001]  
X25166@TSSOP14 [CX1000]  
X25168@SOIC8 [CX1045]  
X25169 [CX0001]  
X25169@TSSOP14 [CX1000]  
X25256 [CX0001]  
X25256@TSSOP20 [CX1000]  
X25320@SOIC8 [CX1045]  
X25323@TSSOP14 [CX1000]  
X25324@TSSOP14 [CX1000]  
X25325@TSSOP14 [CX1000]  
X25328@SOIC8 [CX1045]  
X25329@SOIC8 [CX1045]  
X25330@SOIC8 [CX1045]  
X25401 [CX0001]  
X25640 [CX0001]  
X25642 [CX0001]  
X25642@SOIC8 [CX1045]  
X25643@SOIC14 [CX1016]  
X25645@SOIC14 [CX1016]  
X25649@SOIC14 [CX1016]  
X25650@SOIC14 [CX1016]  
X25650@TSSOP20 [CX1000]  
X25C02@SOIC8 [CX1045]  
X25F008(3V) [CX0001]  
X25F008(3V)@TSSOP14 [CX1016]  
X25F008(5V) [CX0001]  
X25F008(5V)@TSSOP14 [CX1016]  
X25F016(3V) [CX0001]  
X25F016(3V)@TSSOP14 [CX1016]  
X25F016(5V) [CX0001]  
X25F016(5V)@TSSOP14 [CX1016]  
X25F032(3V) [CX0001]  
X25F032(3V)@TSSOP14 [CX1016]  
X25F032(5V) [CX0001]  
X25F032(5V)@TSSOP14 [CX1016]  
X25F047(3V) [CX0001]  
X25F047(3V)@SOIC8 [CX1045]  
X25F047(5V) [CX0001]  
X25F047(5V)@SOIC8 [CX1045]  
X25F064(3V) [CX0001]

X25F064(3V)@SOIC8 [CX1045]  
X25F064(3V)@TSSOP20 [CX1033]  
X25F064(5V)@SOIC8 [CX1045]  
X25F064(5V)@TSSOP20 [CX1033]  
X25F087(3V)@MSOP8 [CX1015]  
X25F087(3V)@TSSOP8 [CX1000]  
X25F087(5V)@MSOP8 [CX1015]  
X25F087(5V)@TSSOP8 [CX1000]  
X25F128(3V)@SOIC16 [CX1016]  
X25F128(5V)@SOIC16 [CX1016]  
X28010@PLCC32 [CX2032]  
X2804A [CX0001]  
X2804A(MB) [CX0001]  
X2816A@PLCC32 [CX2032]  
X2816B@PLCC32 [CX2032]  
X2816BI@PLCC32 [CX2032]  
X2816C [CX0001]  
X28256 [CX0001]  
X28256I [CX0001]  
X2864A [CX0001]  
X2864A(I)@PLCC32 [CX2032]  
X2864A(M)@PLCC32 [CX2032]  
X2864A(MB)@PLCC32 [CX2032]  
X2864A(T)@PLCC32 [CX2032]  
X2864B [CX0001]  
X2864B(I)@PLCC32 [CX2032]  
X2864B(M)@PLCC32 [CX2032]  
X2864H [CX0001]  
X2864H(I)@PLCC32 [CX2032]  
X28C010 [CX0001]  
X28C16A [CX0001]  
X28C16B [CX0001]  
X28C16C [CX0001]  
X28C256 [CX0001]  
X28C256@TSOP28 [CX1024]  
X28C512@PLCC32 [CX2032]  
X28C513 [CX0001]  
X28C64 [CX0001]  
X28C64@SOIC28 [CX1033]  
X28HC16 [CX0001]  
X28HC16@SOIC24 [CX1033]  
X28HC256@PLCC32 [CX2032]  
X28HC256@TSOP28 [CX1024]  
X28HC64@PLCC32 [CX2032]  
X28HC64@TSOP28 [CX1024]  
X28LC512@PLCC32 [CX2032]  
X28LC513@PLCC32 [CX2032]  
X28VC256@PLCC32 [CX2032]  
X40231@SOIC16 [CX1033]  
X40235@SOIC16 [CX1033]  
X40239@SOIC16 [CX1033]  
X4043@MSOP8 [CX1000]  
X40430@SOIC14 [CX1033]  
X40431@SOIC14 [CX1033]  
X40434@SOIC14 [CX1033]  
X40435@SOIC14 [CX1033]  
X4045 [CX0001]  
X4045@SOIC8 [CX1045]  
X5043@MSOP8 [CX1015]  
X25F064(3V)@TSSOP14 [CX1016]  
X25F064(5V) [CX0001]  
X25F064(5V)@TSSOP14 [CX1016]  
X25F087(3V) [CX0001]  
X25F087(3V)@SOIC8 [CX1045]  
X25F087(5V) [CX0001]  
X25F087(5V)@SOIC8 [CX1045]  
X25F128(3V) [CX0001]  
X25F128(5V) [CX0001]  
X28010 [CX0001]  
X28010@TSOP32 [CX1002]  
X2804A(I) [CX0001]  
X2816A [CX0001]  
X2816B [CX0001]  
X2816BI [CX0001]  
X2816BMB [CX0001]  
X2816C@PLCC32 [CX2032]  
X28256@PLCC32 [CX2032]  
X28256I@PLCC32 [CX2032]  
X2864A(I) [CX0001]  
X2864A(M) [CX0001]  
X2864A(MB) [CX0001]  
X2864A(T) [CX0001]  
X2864A@PLCC32 [CX2032]  
X2864B(I) [CX0001]  
X2864B(M) [CX0001]  
X2864B@PLCC32 [CX2032]  
X2864H(I) [CX0001]  
X2864H@PLCC32 [CX2032]  
X28C010@PLCC32 [CX2032]  
X28C16A@PLCC32 [CX2032]  
X28C16B@PLCC32 [CX2032]  
X28C16C@PLCC32 [CX2032]  
X28C256@PLCC32 [CX2032]  
X28C512 [CX0001]  
X28C512@TSOP40 [CX1006]  
X28C513@PLCC32 [CX2032]  
X28C64@PLCC32 [CX2032]  
X28C64@TSOP28 [CX1024]  
X28HC16@PLCC32 [CX2032]  
X28HC256 [CX0001]  
X28HC256@SOIC28 [CX1033]  
X28HC64 [CX0001]  
X28HC64@SOIC28 [CX1033]  
X28LC512 [CX0001]  
X28LC513 [CX0001]  
X28VC256 [CX0001]  
X28VC256@TSOP28 [CX1024]  
X40233@SOIC16 [CX1033]  
X40237@SOIC16 [CX1033]  
X4043 [CX0001]  
X4043@SOIC8 [CX1045]  
X40430@TSSOP14 [CX1000]  
X40431@TSSOP14 [CX1000]  
X40434@TSSOP14 [CX1000]  
X40435@TSSOP14 [CX1000]  
X4045@MSOP8 [CX1000]  
X5043 [CX0001]  
X5043@SOIC8 [CX1045]

X5043@TSSOP14 [CX1000]	X5045 [CX0001]
X5045@MSOP8 [CX1015]	X5045@SOIC8 [CX1045]
X5045@TSSOP14 [CX1000]	X5083 [CX0001]
X5083@SOIC8 [CX1045]	X5083@TSSOP8 [CX1000]
X5163 [CX0001]	X5163@SOIC8 [CX1045]
X5163@TSSOP14 [CX1000]	X51638 [CX0001]
X51638@SOIC8 [CX1045]	X51638@TSSOP14 [CX1000]
X5165 [CX0001]	X5165@SOIC8 [CX1045]
X5165@TSSOP14 [CX1000]	X5168 [CX0001]
X5168@SOIC8 [CX1045]	X5168@TSSOP14 [CX1000]
X5169 [CX0001]	X5169@SOIC8 [CX1045]
X5169@TSSOP14 [CX1000]	X5323 [CX0001]
X5323@SOIC8 [CX1045]	X5323@TSSOP14 [CX1000]
X5325 [CX0001]	X5325@SOIC8 [CX1045]
X5325@TSSOP14 [CX1000]	X5328 [CX0001]
X5328@SOIC8 [CX1045]	X5328@TSSOP14 [CX1000]
X5329 [CX0001]	X5329@SOIC8 [CX1045]
X5329@TSSOP14 [CX1000]	X5643 [CX0001]
X5643@SOIC14	X5643@SOIC8 [CX1045]
X5643@TSSOP20 [CX1000]	X5645 [CX0001]
X5645@SOIC14 [CX1016]	X5645@SOIC8 [CX1045]
X5645@TSSOP20 [CX1000]	X5648 [CX0001]
X5648@SOIC14 [CX1016]	X5649
X5649@SOIC14 [CX1016]	X68C64 [CX0001]
X68C64@SOIC24 [CX1033]	X76F041 [CX0001]
X76F041(3) [CX0001]	X76F041(3)@SOIC8 [CX1044]
X76F041@SOIC8 [CX1044]	X76F101 [CX0001]
X76F101@SOIC8 [CX1045]	X76F400@SOIC8 [CX1000]
X76F400@TSSOP8 [CX1000]	X86C64 [CX0001]
X86C64@SOIC24 [CX1033]	X88064 [CX0001]
X88064@SOIC24 [CX1033]	X88C64 [CX0001]
X88C64@SOIC24 [CX1033]	X88C75 [CX0001]
XD2210 [CX0001]	XD2210@SOIC16 [CX1033]
XM28C010 [CX0001]	XM28C020 [CX0001]
XM28C040 [CX0001]	

## XILINX

### E (E) PROM/FRAM/NVRAM

XC1701 [CX0001]	XC1701@PLCC20 [CX2020]
XC1701@PLCC44 [CX2044]	XC1701@SOIC20 [CX1033]
XC1701L [CX0001]	XC1701L@PLCC20 [CX2020]
XC1701L@PLCC44 [CX2044]	XC1701L@SOIC20 [CX1033]
XC1702L@PLCC44 [CX2044]	XC1702L@TQFP44 [CX3005]
XC1704L@PLCC44 [CX2044]	XC1704L@TQFP44 [CX3005]
XC17128D [CX0001]	XC17128D@PLCC20 [CX2020]
XC17128D@SOIC8 [CX1045]	XC17128D@VOIC8 [CX1045]
XC17128E [CX0001]	XC17128E@PLCC20 [CX2020]
XC17128E@VOIC8 [CX1045]	XC17128EL [CX0001]
XC17128EL@PLCC20 [CX2020]	XC17128EL@VOIC8 [CX1045]
XC17128L [CX0001]	XC17128L@PLCC20 [CX2020]
XC17128L@SOIC8 [CX1045]	XC17128L@VOIC8 [CX1045]
XC17128X [CX0001]	XC17128X@PLCC20 [CX2020]
XC17128X@SOIC8 [CX1045]	XC17128X@VOIC8 [CX1045]
XC1718D [CX0001]	XC1718D@PLCC20 [CX2020]
XC1718D@SOIC8 [CX1045]	XC1718D@VOIC8 [CX1045]
XC1718L [CX0001]	XC1718L@PLCC20 [CX2020]

XC1718L@SOIC8 [CX1045]  
XC17256D [CX0001]  
XC17256D@SOIC8 [CX1045]  
XC17256E [CX0001]  
XC17256E@VOIC8 [CX1045]  
XC17256EL@PLCC20 [CX2020]  
XC17256L [CX0001]  
XC17256L@SOIC8 [CX1045]  
XC17256X [CX0001]  
XC17256X@SOIC8 [CX1045]  
XC1736A [CX0001]  
XC1736D [CX0001]  
XC1736D@SOIC8 [CX1045]  
XC1736E [CX0001]  
XC1736E@SOIC8 [CX1045]  
XC17512L [CX0001]  
XC17512L@PLCC44 [CX2044]  
XC1765D [CX0001]  
XC1765D@SOIC8 [CX1045]  
XC1765E [CX0001]  
XC1765E@SOIC8 [CX1045]  
XC1765EL [CX0001]  
XC1765EL@SOIC8 [CX1045]  
XC1765L [CX0001]  
XC1765L@SOIC8 [CX1045]  
XC1765X [CX0001]  
XC1765X@SOIC8 [CX1045]  
XC17S05 [CX0001]  
XC17S05XL(L) [CX0001]  
XC17S10 [CX0001]  
XC17S100A [CX0001]  
XC17S100A@SOIC8 [CX1045]  
XC17S100XL(L)@SOIC20 [CX1033]  
XC17S10XL(L)@SOIC8 [CX1045]  
XC17S150A@SOIC20 [CX1033]  
XC17S150XL(L) [CX0001]  
XC17S15A [CX0001]  
XC17S15A@SOIC8 [CX1045]  
XC17S20@SOIC8 [CX1045]  
XC17S200A@SOIC8 [CX1045]  
XC17S20XL(L) [CX0001]  
XC17S30 [CX0001]  
XC17S300A@TQFP44 [CX3005]  
XC17S30A@SOIC20 [CX1033]  
XC17S30XL(L) [CX0001]  
XC17S40 [CX0001]  
XC17S40XL(L) [CX0001]  
XC17S50A [CX0001]  
XC17S50A@SOIC8 [CX1045]  
XC17S50XL(L)@SOIC20 [CX1033]  
XC17V01@SOIC20 [CX1033]  
XC17V02@PLCC20 [CX2020]  
XC17V02@TQFP44 [CX3005]  
XC17V04@PLCC44 [CX2044]  
XC17V08@PLCC44 [CX2044]  
XC17V16@PLCC44 [CX2044]  
XC18V01@PLCC20 [CX2020]  
XC18V01@TQFP44 [CX3003]  
XC18V02@TQFP44 [CX3003]

XC1718L@VOIC8 [CX1045]  
XC17256D@PLCC20 [CX2020]  
XC17256D@VOIC8 [CX1045]  
XC17256E@PLCC20 [CX2020]  
XC17256EL [CX0001]  
XC17256EL@VOIC8 [CX1045]  
XC17256L@PLCC20 [CX2020]  
XC17256L@VOIC8 [CX1045]  
XC17256X@PLCC20 [CX2020]  
XC17256X@VOIC8 [CX1045]  
XC1736A@SOIC8 [CX1016]  
XC1736D@PLCC20 [CX2020]  
XC1736D@VOIC8 [CX1045]  
XC1736E@PLCC20 [CX2020]  
XC1736E@VOIC8 [CX1045]  
XC17512L@PLCC20 [CX2020]  
XC17512L@SOIC20 [CX1033]  
XC1765D@PLCC20 [CX2020]  
XC1765D@VOIC8 [CX1045]  
XC1765E@PLCC20 [CX2020]  
XC1765E@VOIC8 [CX1045]  
XC1765EL@PLCC20 [CX2020]  
XC1765EL@VOIC8 [CX1045]  
XC1765L@PLCC20 [CX2020]  
XC1765L@VOIC8 [CX1045]  
XC1765X@PLCC20 [CX2020]  
XC1765X@VOIC8 [CX1045]  
XC17S05@SOIC8 [CX1045]  
XC17S05XL(L)@SOIC8 [CX1045]  
XC17S10@SOIC8 [CX1045]  
XC17S100A@SOIC20 [CX1033]  
XC17S100XL(L) [CX0001]  
XC17S10XL(L) [CX0001]  
XC17S150A [CX0001]  
XC17S150A@SOIC8 [CX1045]  
XC17S150XL(L)@SOIC20 [CX1033]  
XC17S15A@SOIC20 [CX1033]  
XC17S20 [CX0001]  
XC17S200A [CX0001]  
XC17S200A@TQFP44 [CX3005]  
XC17S20XL(L)@SOIC8 [CX1045]  
XC17S30@SOIC8 [CX1045]  
XC17S30A [CX0001]  
XC17S30A@SOIC8 [CX1045]  
XC17S30XL(L)@SOIC8 [CX1045]  
XC17S40@SOIC20 [CX1033]  
XC17S40XL(L)@SOIC20 [CX1033]  
XC17S50A@SOIC20 [CX1033]  
XC17S50XL(L) [CX0001]  
XC17V01@PLCC20 [CX2020]  
XC17V01@SOIC8 [CX1045]  
XC17V02@PLCC44 [CX2044]  
XC17V04@PLCC20 [CX2020]  
XC17V04@TQFP44 [CX3005]  
XC17V08@TQFP44 [CX3005]  
XC17V16@TQFP44 [CX3005]  
XC18V01@SOIC20 [CX1033]  
XC18V02@PLCC44 [CX2144]  
XC18V04@PLCC44 [CX2144]



XC18V04@TQFP44 [CX3003]  
XC18V256@SOIC20 [CX1033]  
XC18V512@PLCC20 [CX2020]  
XC18V512@TQFP44 [CX3003]  
XCF01S(VO)@TSSOP20(ISP) [CX0001]  
XCF01S(VOG)@TSSOP20(ISP) [CX0001]  
XCF02S(VO)@TSSOP20 [CX1000]  
XCF02S(VOG)@TSSOP20 [CX1000]  
XCF02S(VOG)@TSSOP20(ISP) [CX0001]  
XCF04S(VO)@TSSOP20 [CX1000]  
XCF04S(VOG)@TSSOP20 [CX1000]  
XCF04S(VOG)@TSSOP20(ISP) [CX0001]  
XCF08P(FS)@FBGA48 [CX5022]  
XCF08P(FSG)@FBGA48 [CX5022]  
XCF08P(VO)@TSOP48 [CX1004]  
XCF08P(VOG)@TSOP48 [CX1004]  
XCF16P(FS)@FBGA48 [CX5022]  
XCF16P(FSG)@FBGA48 [CX5022]  
XCF16P(VO)@TSOP48 [CX1004]  
XCF16P(VOG)@TSOP48 [CX1004]  
XCF32P(FS)@FBGA48 [CX5022]  
XCF32P(FSG)@FBGA48 [CX5022]  
XCF32P(VO)@TSOP48 [CX1004]  
XCF32P(VOG)@TSOP48 [CX1004]

XC18V256@PLCC20 [CX2020]  
XC18V256@TQFP44 [CX3003]  
XC18V512@SOIC20 [CX1033]  
XCF01S(VO)@TSSOP20 [CX1000]  
XCF01S(VOG)@TSSOP20 [CX1000]  
XCF02S(VO)@TSSOP20(ISP) [CX0001]  
XCF04S(VO)@TSSOP20(ISP) [CX0001]  
XCF08P(FS)@FBGA48(ISP) [CX0001]  
XCF08P(FSG)@FBGA48(ISP) [CX0001]  
XCF08P(VO)@TSOP48(ISP) [CX0001]  
XCF08P(VOG)@TSOP48(ISP) [CX0001]  
XCF16P(FS)@FBGA48(ISP) [CX0001]  
XCF16P(FSG)@FBGA48(ISP) [CX0001]  
XCF16P(VO)@TSOP48(ISP) [CX0001]  
XCF16P(VOG)@TSOP48(ISP) [CX0001]  
XCF32P(FS)@FBGA48(ISP) [CX0001]  
XCF32P(FSG)@FBGA48(ISP) [CX0001]  
XCF32P(VO)@TSOP48(ISP) [CX0001]  
XCF32P(VOG)@TSOP48(ISP) [CX0001]

## PLD

PZ3032C@PLCC44 [CX2044]  
PZ3032N@PLCC44 [CX2044]  
XC2C128@TQFP100 [CX3021]  
XC2C32@CP56 [CX5102]  
XC2C32@VQFP44 [CX3003]  
XC2C32A@PLCC44 [CX2044]  
XC2C32A@VQFP44 [CX3003]  
XC7318@PQFP44 [CX3003]  
XC7336@PLCC44 [CX2044]  
XC7336@VQFP44 [CX3003]  
XC7336Q@PQFP44 [CX3003]  
XC7354@PLCC44 [CX2044]  
XC7372@PLCC68 [CX2068]  
XC7372@PQFP100 [CX3022]  
XC9536@TQFP44 [CX3003]  
XC9536XL@PLCC44 [CX2044]  
XC9536XL@VQFP44 [CX3003]  
XC9536XV@PLCC44 [CX2044]  
XC9572@PLCC44 [CX2044]  
XC9572@PQFP100 [CX3022]  
XC9572@TQFP44 [CX3003]  
XC9572XL@PLCC44 [CX2044]  
XC9572XL@TQFP44 [CX3003]  
XC9572XV@CSP48 [CX5112]  
XC9572XV@TQFP100 [CX3021]  
XCR3032A@PLCC44 [CX2044]  
XCR3032C@PLCC44 [CX2044]  
XCR3032N@PLCC44 [CX2044]  
XCR3032XL@cSbGA48 [CX5112]  
XCR3032XL@TQFP44 [CX3003]

PZ3032C@TQFP44 [CX3003]  
PZ3032N@TQFP44 [CX3003]  
XC2C256@TQFP100 [CX3021]  
XC2C32@PLCC44 [CX2044]  
XC2C32A@CP56 [CX5102]  
XC2C32A@QFG32 [CX4015]  
XC7318@PLCC44 [CX2044]  
XC7318@VQFP44 [CX3003]  
XC7336@PQFP44 [CX3003]  
XC7336Q@PLCC44 [CX2044]  
XC7336Q@VQFP44 [CX3003]  
XC7354@PLCC68 [CX2068]  
XC7372@PLCC84 [CX2084]  
XC9536@PLCC44 [CX2044]  
XC9536XL@CSP48 [CX5112]  
XC9536XL@TQFP64 [CX3011]  
XC9536XV@CSP48 [CX5112]  
XC9536XV@TQFP44 [CX3003]  
XC9572@PLCC84 [CX2084]  
XC9572@TQFP100 [CX3021]  
XC9572XL@CSP48 [CX5112]  
XC9572XL@TQFP100 [CX3021]  
XC9572XL@TQFP64 [CX3011]  
XC9572XV@PLCC44 [CX2044]  
XC9572XV@TQFP44 [CX3003]  
XCR3032A@TQFP44 [CX3003]  
XCR3032C@TQFP44 [CX3003]  
XCR3032N@TQFP44 [CX3003]  
XCR3032XL@PLCC44 [CX2044]  
XCR3512XL@PQFP208 [CX3074]

# XINNOVA

## MICROCONTROLLER

XN89F515 [CX0001]	XN89F515@PLCC44 [CX2044]
XN89F515@TQFP44 [CX3002]	XN89L515 [CX0001]
XN89L515@PLCC44 [CX2044]	XN89L515@TQFP44 [CX3002]
XN89W517 [CX0001]	XN89W517@LQFP48 [CX3007]
XN89W517@PLCC44 [CX2044]	XN89W517@PQFP44 [CX3002]

# XINYANG

## MICROCONTROLLER

ATtiny44A@MLF20 [CX0001]

# XUMARS

## MICROCONTROLLER

HS32423SP28@SOIC28 [CX1033]	HS32423SP28@SOIC28 (ISP) [CX0001]
HS32533SP28@SOIC28 [CX1033]	HS32533SP28@SOIC28 (ISP) [CX0001]

# YMC

## E (E) PROM/FRAM/NVRAM

Y24LC01 [CX0001]	Y24LC01@SOIC8 [CX1045]
Y24LC01@TSSOP8 [CX1059]	Y24LC02 [CX0001]
Y24LC02@SOIC8 [CX1045]	Y24LC02@TSSOP8 [CX1059]
Y24LC02A [CX0001]	Y24LC02A@SOIC8 [CX1045]
Y24LC02A@TSSOP8 [CX1059]	Y24LC04 [CX0001]
Y24LC04@SOIC8 [CX1045]	Y24LC04@TSSOP8 [CX1059]
Y24LC08 [CX0001]	Y24LC08@SOIC8 [CX1045]
Y24LC08@TSSOP8 [CX1059]	Y24LC16 [CX0001]
Y24LC16@SOIC8 [CX1045]	Y24LC16@TSSOP8 [CX1059]
Y24LC32 [CX0001]	Y24LC32@SOIC8 [CX1045]
Y24LC32@TSSOP8 [CX1059]	Y24LC64 [CX0001]
Y24LC64@SOIC8 [CX1045]	Y24LC64@TSSOP8 [CX1059]
Y54LC64	Y54LC64@SOIC8 [CX1045]
Y54LC64@TSSOP8 [CX1000]	Y93LC46(16bit) [CX0001]
Y93LC46(16bit)@SOIC8 [CX1045]	Y93LC46(16bit)@TSSOP8 [CX1059]
Y93LC46-08 [CX0001]	Y93LC46-08-S8 [CX1045]
Y93LC46-08-T8 [CX1059]	Y93LC66(08bit) [CX0001]
Y93LC66(08bit)@SOIC8 [CX1045]	Y93LC66(08bit)@TSSOP8 [CX1059]
Y93LC66(16bit) [CX0001]	Y93LC66(16bit)@SOIC8 [CX1045]
Y93LC66(16bit)@TSSOP8 [CX1059]	Y93LC86(08bit) [CX0001]
Y93LC86(08bit)@SOIC8 [CX1045]	Y93LC86(08bit)@TSSOP8 [CX1059]
Y93LC86(16bit) [CX0001]	Y93LC86(16bit)@SOIC8 [CX1045]
Y93LC86(16bit)@TSSOP8 [CX1059]	

# YSS

## E (E) PROM/FRAM/NVRAM

Y25F05@SOP8 [CX1045]  
Y25F10@SOP8 [CX1045]

Y25F05@VQFN8 [CX4005]  
Y25F10@VQFN8 [CX4005]

## YXLDZ

### E (E) PROM/FRAM/NVRAM

YXL9020F [CX1045]

## ZENTEL

### E (E) PROM/FRAM/NVRAM

A5U1GA31ATS@TSOP48 [CX1004-1]  
A5U2GA31BTS@TSOP48 [CX1004-1]  
A5U8GA31ATS@TSOP48 [CX1004-1]

A5U2GA31ATS@TSOP48 [CX1004-1]  
A5U4GA31ATS@TSOP48 [CX1004-1]

## ZHENGXIN

### E (E) PROM/FRAM/NVRAM

LX24C01 [CX0001]  
LX24C01@TSSOP8 [CX1059]  
LX24C02@SOIC8 [CX1045]  
LX24C04 [CX0001]  
LX24C04@TSSOP8 [CX1059]  
LX24C08@SOIC8 [CX1045]  
LX24C16 [CX0001]  
LX24C16@TSSOP8 [CX1059]

LX24C01@SOIC8 [CX1045]  
LX24C02 [CX0001]  
LX24C02@TSSOP8 [CX1059]  
LX24C04@SOIC8 [CX1045]  
LX24C08 [CX0001]  
LX24C08@TSSOP8 [CX1059]  
LX24C16@SOIC8 [CX1045]

## ZILOG

### MICROCONTROLLER

Z16F2810AG20AG@LQFP64 [CX3011]  
Z16F2810AG20SG@LQFP64 [CX3011]  
Z16F2810FI20EG@QFP80 [CX3019]  
Z16F2810VH20AG@PLCC68 [CX2068]  
Z16F2810VH20SG@PLCC68 [CX2068]  
Z16F2811AL20EG@LQFP100 [CX3043]  
Z16F2811FI20AG@QFP80 [CX3019]  
Z16F2811FI20SG@QFP80 [CX3019]  
Z16F3211AL20EG@LQFP100 [CX3043]  
Z16F3211FI20AG@QFP80 [CX3019]  
Z16F3211FI20SG@QFP80 [CX3019]  
Z16F6411AL20EG@LQFP100 [CX3043]  
Z16F6411FI20AG@QFP80 [CX3019]  
Z16F6411FI20SG@QFP80 [CX3019]  
Z51F3220SKX [CX1034]  
Z86733@PLCC28 [CX2028]  
Z8673312PSC [CX0001]  
Z8673312VSC [CX2028]  
Z86743@PLCC44 [CX2044]  
Z8674312PSC [CX0001]  
Z86C0208PEC [CX0001]

Z16F2810AG20EG@LQFP64 [CX3011]  
Z16F2810FI20AG@QFP80 [CX3019]  
Z16F2810FI20SG@QFP80 [CX3019]  
Z16F2810VH20EG@PLCC68 [CX2068]  
Z16F2811AL20AG@LQFP100 [CX3043]  
Z16F2811AL20SG@LQFP100 [CX3043]  
Z16F2811FI20EG@QFP80 [CX3019]  
Z16F3211AL20AG@LQFP100 [CX3043]  
Z16F3211AL20SG@LQFP100 [CX3043]  
Z16F3211FI20EG@QFP80 [CX3019]  
Z16F6411AL20AG@LQFP100 [CX3043]  
Z16F6411AL20SG@LQFP100 [CX3043]  
Z16F6411FI20EG@QFP80 [CX3019]  
Z51F3220FNX [CX3002]  
Z86733 [CX0001]  
Z86733@SOIC28 [CX1033]  
Z8673312SSC [CX1033]  
Z86743 [CX0001]  
Z8674312FSC [CX3005]  
Z8674312VSC [CX2044]  
Z86C0208PSC [CX0001]

Z86C0208SEC@SOIC18 [CX1033]  
Z86D7308FSC@QFP44 [CX3002]  
Z86D7308PSC [CX0001]  
Z86D8608PSC [CX0001]  
Z86D8608SSG@SOIC28 [CX1033]  
Z86D9808PSC [CX0001]  
Z86D9808SSG@SOIC28 [CX1033]  
Z86E02@SOIC18 [CX1033]  
Z86E0208PEG [CX0001]  
Z86E0208SEG [CX1033]  
Z86E03@SOIC18 [CX1033]  
Z86E0308PEG [CX0001]  
Z86E0308SEG [CX1033]  
Z86E04@SOIC18 [CX1033]  
Z86E0412PEC1903 [CX0001]  
Z86E0412PEG [CX0001]  
Z86E0412PSC1903 [CX0001]  
Z86E0412PSG [CX0001]  
Z86E0412SEC1903 [CX1033]  
Z86E0412SEG [CX1033]  
Z86E0412SSC1903 [CX1033]  
Z86E0412SSG [CX1033]  
Z86E06@SOIC18 [CX1033]  
Z86E07@SOIC18 [CX1033]  
Z86E08@SOIC18 [CX1033]  
Z86E0812PEC1903 [CX0001]  
Z86E0812PEG [CX0001]  
Z86E0812PSC1903 [CX0001]  
Z86E0812PSG [CX0001]  
Z86E0812SEC1903 [CX1033]  
Z86E0812SEG [CX1033]  
Z86E0812SSC1903 [CX1033]  
Z86E0812SSG [CX1033]  
Z86E122@SOIC20 [CX1033]  
Z86E123@SOIC20 [CX1033]  
Z86E124@SOIC20 [CX1033]  
Z86E125@SOIC20 [CX1033]  
Z86E126@SOIC20 [CX1033]  
Z86E132@SOIC28 [CX1033]  
Z86E133@SOIC28 [CX1033]  
Z86E134@SOIC28 [CX1033]  
Z86E135@SOIC28 [CX1033]  
Z86E136@SOIC28 [CX1033]  
Z86E142@TQFP44 [CX3005]  
Z86E143@TQFP44 [CX3005]  
Z86E144@TQFP44 [CX3005]  
Z86E145@TQFP44 [CX3005]  
Z86E146@TQFP44 [CX3005]  
Z86E21 [CX0001]  
Z86E21@TQFP44 [CX3005]  
Z86E2112@PLCC44 [CX2044]  
Z86E2116 [CX0001]  
Z86E2116@TQFP44 [CX3005]  
Z86E23@PLCC44 [CX2044]  
Z86E2312 [CX0001]  
Z86E2312@TQFP44 [CX3005]  
Z86E2316@PLCC44 [CX2044]  
Z86E3016PEC [CX0001]  
Z86E3016PSC [CX0001]

Z86C0208SSC@SOIC18 [CX1033]  
Z86D7308HSC@SSOP48 [CX1028]  
Z86D7308VSC@PLCC44 [CX2044]  
Z86D8608SSC@SOIC28 [CX1033]  
Z86D93@PLCC68 [CX0001]  
Z86D9808SSC@SOIC28 [CX1033]  
Z86E02 [CX0001]  
Z86E0208PEC [CX0001]  
Z86E0208SEC [CX1033]  
Z86E03 [CX0001]  
Z86E0308PEC [CX0001]  
Z86E0308SEC [CX1033]  
Z86E04 [CX0001]  
Z86E0412PEC [CX0001]  
Z86E0412PEC2004 [CX0001]  
Z86E0412PSC1866 [CX0001]  
Z86E0412PSC2004 [CX0001]  
Z86E0412SEC [CX1033]  
Z86E0412SEC2004 [CX1033]  
Z86E0412SSC1866 [CX1033]  
Z86E0412SSC2004 [CX1033]  
Z86E06 [CX0001]  
Z86E07 [CX0001]  
Z86E08 [CX0001]  
Z86E0812PEC [CX0001]  
Z86E0812PEC2004 [CX0001]  
Z86E0812PSC1866 [CX0001]  
Z86E0812PSC2004 [CX0001]  
Z86E0812SEC [CX1033]  
Z86E0812SEC2004 [CX1033]  
Z86E0812SSC1866 [CX1033]  
Z86E0812SSC2004 [CX1033]  
Z86E122 [CX0001]  
Z86E123 [CX0001]  
Z86E124 [CX0001]  
Z86E125 [CX0001]  
Z86E126 [CX0001]  
Z86E132 [CX0001]  
Z86E133 [CX0001]  
Z86E134 [CX0001]  
Z86E135 [CX0001]  
Z86E136 [CX0001]  
Z86E142 [CX0001]  
Z86E143 [CX0001]  
Z86E144 [CX0001]  
Z86E145 [CX0001]  
Z86E146 [CX0001]  
Z86E15 [CX0001]  
Z86E21@PLCC44 [CX2044]  
Z86E2112 [CX0001]  
Z86E2112@TQFP44 [CX3005]  
Z86E2116@PLCC44 [CX2044]  
Z86E23 [CX0001]  
Z86E23@TQFP44 [CX3005]  
Z86E2312@PLCC44 [CX2044]  
Z86E2316 [CX0001]  
Z86E2316@TQFP44 [CX3005]  
Z86E3016PEG [CX0001]  
Z86E3016PSG [CX0001]

Z86E3016SEC@SOIC28 [CX1033]  
Z86E3016SSC@SOIC28 [CX1033]  
Z86E3016VEC@PLCC28 [CX2028]  
Z86E3016VSC@PLCC28 [CX2028]  
Z86E3116PEC [CX0001]  
Z86E3116PSC [CX0001]  
Z86E3116SEC@SOIC28 [CX1033]  
Z86E3116SSC@SOIC28 [CX1033]  
Z86E3116VEC@PLCC28 [CX2028]  
Z86E3116VSC@PLCC28 [CX2028]  
Z86E33 [CX0001]  
Z86E33@SOIC28 [CX1033]  
Z86E3312SSC [CX1033]  
Z86E34 [CX0001]  
Z86E34@SOIC28 [CX1033]  
Z86E3412SSC [CX1033]  
Z86E4016FEC@TQFP44 [CX3066]  
Z86E4016FSC@TQFP44 [CX3066]  
Z86E4016PEC [CX0001]  
Z86E4016PSC [CX0001]  
Z86E4016VEC@PLCC44 [CX2044]  
Z86E4016VSC@PLCC44 [CX2044]  
Z86E43 [CX0001]  
Z86E43@TQFP44 [CX3005]  
Z86E4312PSC [CX0001]  
Z86E44 [CX0001]  
Z86E44@TQFP44 [CX3005]  
Z86E4412PSC [CX0001]  
Z86E6116ASC [CX3005]  
Z86E6116PSC [CX0001]  
Z86E6116VSC@PLCC44 [CX2044]  
Z86E6120ASC [CX3005]  
Z86E6120PSC [CX0001]  
Z86E6120VSC@PLCC44 [CX2044]  
Z86E61FSC@TQFP44 [CX3005]  
Z86E61PSC [CX0001]  
Z86E61VSC@PLCC44 [CX2044]  
Z86E6316ASC [CX3005]  
Z86E6316PSC [CX0001]  
Z86E6316VSC@PLCC44 [CX2044]  
Z86E6320ASC [CX3005]  
Z86E6320PSC [CX0001]  
Z86E6320VSC@PLCC44 [CX2044]  
Z86E63FSC@TQFP44 [CX3005]  
Z86E63PSC [CX0001]  
Z86E63VSC@PLCC44 [CX2044]  
Z86E72 [CX0001]  
Z86E72@TQFP44 [CX3005]  
Z86E7216@PLCC44 [CX2044]  
Z86E73 [CX0001]  
Z86E73@TQFP44 [CX3005]  
Z86E7316@PLCC44 [CX2044]  
Z86E83 [CX0001]  
Z86E83@SOIC28 [CX1033]  
Z86E8316@PLCC28 [CX2028]  
Z86L0208PEC [CX0001]  
Z86L0208SEC@SOIC18 [CX1033]  
Z89371 [CX0001]  
Z89371@TQFP44 [CX3005]

Z86E3016SEG [CX1033]  
Z86E3016SSG [CX1033]  
Z86E3016VEG [CX2028]  
Z86E3016VSG@PLCC28 [CX2028]  
Z86E3116PEG [CX0001]  
Z86E3116PSG [CX0001]  
Z86E3116SEG [CX1033]  
Z86E3116SSG [CX1033]  
Z86E3116VEG [CX2028]  
Z86E3116VSG@PLCC28 [CX2028]  
Z86E33@PLCC28 [CX2028]  
Z86E3312PSC [CX0001]  
Z86E3312VSC [CX2028]  
Z86E34@PLCC28 [CX2028]  
Z86E3412PSC [CX0001]  
Z86E3412VSC [CX2028]  
Z86E4016FEG [CX3066]  
Z86E4016FSG [CX3066]  
Z86E4016PEG [CX0001]  
Z86E4016PSG [CX0001]  
Z86E4016VEG [CX2044]  
Z86E4016VSG@PLCC44 [CX2044]  
Z86E43@PLCC44 [CX2044]  
Z86E4312FSC [CX3005]  
Z86E4312VSC [CX2044]  
Z86E44@PLCC44 [CX2044]  
Z86E4412FSC [CX3005]  
Z86E4412VSC [CX2044]  
Z86E6116ASG@TQFP44 [CX3005]  
Z86E6116PSG [CX0001]  
Z86E6116VSG [CX2044]  
Z86E6120ASG@TQFP44 [CX3005]  
Z86E6120PSG [CX0001]  
Z86E6120VSG [CX2044]  
Z86E61FSG [CX3005]  
Z86E61PSG [CX0001]  
Z86E61VSG [CX2044]  
Z86E6316ASG@TQFP44 [CX3005]  
Z86E6316PSG [CX0001]  
Z86E6316VSG [CX2044]  
Z86E6320ASG@TQFP44 [CX3005]  
Z86E6320PSG [CX0001]  
Z86E6320VSG [CX2044]  
Z86E63FSG [CX3005]  
Z86E63PSG [CX0001]  
Z86E63VSG [CX2044]  
Z86E72@PLCC44 [CX2044]  
Z86E7216 [CX0001]  
Z86E7216@TQFP44 [CX3005]  
Z86E73@PLCC44 [CX2044]  
Z86E7316 [CX0001]  
Z86E7316@TQFP44 [CX3005]  
Z86E83@PLCC28 [CX2028]  
Z86E8316 [CX0001]  
Z86E8316@SOIC28 [CX1033]  
Z86L0208PSC [CX0001]  
Z86L0208SSC@SOIC18 [CX1033]  
Z89371@PLCC44 [CX2044]  
Z89371B [CX0001]

Z89371B@PLCC44 [CX2044]  
Z8E00010HEC@SSOP20 [CX1001]  
Z8E00010PEC [CX0001]  
Z8E00010SEC@SOIC18 [CX1033]  
Z8E00010SSG@SOIC18 [CX1033]  
Z8E00110HSC@SSOP20 [CX1001]  
Z8E00110PSC [CX0001]  
Z8E00110SSC@SOIC18 [CX1033]  
Z8F0113HH005EC@SSOP20 [CX1026]  
Z8F0113HH005SC@SSOP20 [CX1026]  
Z8F0113HJ005EC@SSOP28 [CX1026]  
Z8F0113HJ005SC@SSOP28 [CX1026]  
Z8F0113PB005EC [CX0001]  
Z8F0113PB005SC [CX0001]  
Z8F0113PH005EC [CX0001]  
Z8F0113PH005SC [CX0001]  
Z8F0113PJ005EC [CX0001]  
Z8F0113PJ005SC [CX0001]  
Z8F0113QB005EC@QFN8 [CX4005]  
Z8F0113QB005SC@QFN8 [CX4005]  
Z8F0113SB005EC@SOIC8 [CX1045]  
Z8F0113SB005SC@SOIC8 [CX1045]  
Z8F0113SH005EC@SOIC20 [CX1033]  
Z8F0113SH005SC@SOIC20 [CX1033]  
Z8F0113SJ005EC@SOIC28 [CX1033]  
Z8F0113SJ005SC@SOIC28 [CX1033]  
Z8F011AHH020EC@SSOP20 [CX1026]  
Z8F011AHH020SC@SSOP20 [CX1026]  
Z8F011AHJ020EC@SSOP28 [CX1026]  
Z8F011AHJ020SC@SSOP28 [CX1026]  
Z8F011APB020EC [CX0001]  
Z8F011APB020SC [CX0001]  
Z8F011APH020EC [CX0001]  
Z8F011APH020SC [CX0001]  
Z8F011APJ020EC [CX0001]  
Z8F011APJ020SC [CX0001]  
Z8F011AQB020EC@QFN8 [CX4005]  
Z8F011AQB020SC@QFN8 [CX4005]  
Z8F011ASB020EC@SOIC8 [CX1045]  
Z8F011ASB020SC@SOIC8 [CX1045]  
Z8F011ASH020EC@SOIC20 [CX1033]  
Z8F011ASH020SC@SOIC20 [CX1033]  
Z8F011ASJ020EC@SOIC28 [CX1033]  
Z8F011ASJ020SC@SOIC28 [CX1033]  
Z8F0123HH005EC@SSOP20 [CX1026]  
Z8F0123HH005SC@SSOP20 [CX1026]  
Z8F0123HJ005EC@SSOP28 [CX1026]  
Z8F0123HJ005SC@SSOP28 [CX1026]  
Z8F0123PB005EC [CX0001]  
Z8F0123PB005SC [CX0001]  
Z8F0123PH005EC [CX0001]  
Z8F0123PH005SC [CX0001]  
Z8F0123PJ005EC [CX0001]  
Z8F0123PJ005SC [CX0001]  
Z8F0123QB005EC@QFN8 [CX4005]  
Z8F0123QB005SC@QFN8 [CX4005]  
Z8F0123SB005EC@SOIC8 [CX1045]  
Z8F0123SB005SC@SOIC8 [CX1045]  
Z8F0123SH005EC@SOIC20 [CX1033]

Z89371B@TQFP44 [CX3005]  
Z8E00010HSC@SSOP20 [CX1001]  
Z8E00010PSC [CX0001]  
Z8E00010SSC@SOIC18 [CX1033]  
Z8E00110HEC@SSOP20 [CX1001]  
Z8E00110PEC [CX0001]  
Z8E00110SEC@SOIC18 [CX1033]  
Z8E00110SSG@SOIC18 [CX1033]  
Z8F0113HH005EG@SSOP20 [CX1026]  
Z8F0113HH005SG@SSOP20 [CX1026]  
Z8F0113HJ005EG@SSOP28 [CX1026]  
Z8F0113HJ005SG@SSOP28 [CX1026]  
Z8F0113PB005EG [CX0001]  
Z8F0113PB005SG [CX0001]  
Z8F0113PH005EG [CX0001]  
Z8F0113PH005SG [CX0001]  
Z8F0113PJ005EG [CX0001]  
Z8F0113PJ005SG [CX0001]  
Z8F0113QB005EG@QFN8 [CX4005]  
Z8F0113QB005SG@QFN8 [CX4005]  
Z8F0113SB005EG@SOIC8 [CX1045]  
Z8F0113SB005SG@SOIC8 [CX1045]  
Z8F0113SH005EG@SOIC20 [CX1033]  
Z8F0113SH005SG@SOIC20 [CX1033]  
Z8F0113SJ005EG@SOIC28 [CX1033]  
Z8F0113SJ005SG@SOIC28 [CX1033]  
Z8F011AHH020EG@SSOP20 [CX1026]  
Z8F011AHH020SG@SSOP20 [CX1026]  
Z8F011AHJ020EG@SSOP28 [CX1026]  
Z8F011AHJ020SG@SSOP28 [CX1026]  
Z8F011APB020EG [CX0001]  
Z8F011APB020SG [CX0001]  
Z8F011APH020EG [CX0001]  
Z8F011APH020SG [CX0001]  
Z8F011APJ020EG [CX0001]  
Z8F011APJ020SG [CX0001]  
Z8F011AQB020EG@QFN8 [CX4005]  
Z8F011AQB020SG@QFN8 [CX4005]  
Z8F011ASB020EG@SOIC8 [CX1045]  
Z8F011ASB020SG@SOIC8 [CX1045]  
Z8F011ASH020EG@SOIC20 [CX1033]  
Z8F011ASH020SG@SOIC20 [CX1033]  
Z8F011ASJ020EG@SOIC28 [CX1033]  
Z8F011ASJ020SG@SOIC28 [CX1033]  
Z8F0123HH005EG@SSOP20 [CX1026]  
Z8F0123HH005SG@SSOP20 [CX1026]  
Z8F0123HJ005EG@SSOP28 [CX1026]  
Z8F0123HJ005SG@SSOP28 [CX1026]  
Z8F0123PB005EG [CX0001]  
Z8F0123PB005SG [CX0001]  
Z8F0123PH005EG [CX0001]  
Z8F0123PH005SG [CX0001]  
Z8F0123PJ005EG [CX0001]  
Z8F0123PJ005SG [CX0001]  
Z8F0123QB005EG@QFN8 [CX4005]  
Z8F0123QB005SG@QFN8 [CX4005]  
Z8F0123SB005EG@SOIC8 [CX1045]  
Z8F0123SB005SG@SOIC8 [CX1045]  
Z8F0123SH005EG@SOIC20 [CX1033]

Z8F0123SH005SC@SOIC20 [CX1033]	Z8F0123SH005SG@SOIC20 [CX1033]
Z8F0123SJ005EC@SOIC28 [CX1033]	Z8F0123SJ005EG@SOIC28 [CX1033]
Z8F0123SJ005SC@SOIC28 [CX1033]	Z8F0123SJ005SG@SOIC28 [CX1033]
Z8F012AHH020EC@SSOP20 [CX1026]	Z8F012AHH020EG@SSOP20 [CX1026]
Z8F012AHH020SC@SSOP20 [CX1026]	Z8F012AHH020SG@SSOP20 [CX1026]
Z8F012AHJ020EC@SSOP28 [CX1026]	Z8F012AHJ020EG@SSOP28 [CX1026]
Z8F012AHJ020SC@SSOP28 [CX1026]	Z8F012AHJ020SG@SSOP28 [CX1026]
Z8F012APB020EC [CX0001]	Z8F012APB020EG [CX0001]
Z8F012APB020SC [CX0001]	Z8F012APB020SG [CX0001]
Z8F012APH020EC [CX0001]	Z8F012APH020EG [CX0001]
Z8F012APH020SC [CX0001]	Z8F012APH020SG [CX0001]
Z8F012APJ020EC [CX0001]	Z8F012APJ020EG [CX0001]
Z8F012APJ020SC [CX0001]	Z8F012APJ020SG [CX0001]
Z8F012AQB020EC@QFN8 [CX4005]	Z8F012AQB020EG@QFN8 [CX4005]
Z8F012AQB020SC@QFN8 [CX4005]	Z8F012AQB020SG@QFN8 [CX4005]
Z8F012ASB020EC@SOIC8 [CX1045]	Z8F012ASB020EG@SOIC8 [CX1045]
Z8F012ASB020SC@SOIC8 [CX1045]	Z8F012ASB020SG@SOIC8 [CX1045]
Z8F012ASH020EC@SOIC20 [CX1033]	Z8F012ASH020EG@SOIC20 [CX1033]
Z8F012ASH020SC@SOIC20 [CX1033]	Z8F012ASH020SG@SOIC20 [CX1033]
Z8F012ASJ020EC@SOIC28 [CX1033]	Z8F012ASJ020EG@SOIC28 [CX1033]
Z8F012ASJ020SC@SOIC28 [CX1033]	Z8F012ASJ020SG@SOIC28 [CX1033]
Z8F0130HH020EG@SSOP20 [CX1026]	Z8F0130HH020SG@SSOP20 [CX1026]
Z8F0130HJ020EG@SSOP28 [CX1026]	Z8F0130HJ020SG@SSOP28 [CX1026]
Z8F0130PH020EG [CX0001]	Z8F0130PH020SG [CX0001]
Z8F0130PJ020EG [CX0001]	Z8F0130PJ020SG [CX0001]
Z8F0130QH020EG@QFN20 [CX4025]	Z8F0130QH020SG@QFN20 [CX4025]
Z8F0130QJ020EG@QFN28 [CX4013]	Z8F0130QJ020SG@QFN28 [CX4013]
Z8F0130SH020EG@SOIC20 [CX1033]	Z8F0130SH020SG@SOIC20 [CX1033]
Z8F0130SJ020EG@SOIC28 [CX1033]	Z8F0130SJ020SG@SOIC28 [CX1033]
Z8F0131HH020EG@SSOP20 [CX1026]	Z8F0131HH020SG@SSOP20 [CX1026]
Z8F0131HJ020EG@SSOP28 [CX1026]	Z8F0131HJ020SG@SSOP28 [CX1026]
Z8F0131PH020EG [CX0001]	Z8F0131PH020SG [CX0001]
Z8F0131PJ020EG [CX0001]	Z8F0131PJ020SG [CX0001]
Z8F0131QH020EG@QFN20 [CX4025]	Z8F0131QH020SG@QFN20 [CX4025]
Z8F0131QJ020EG@QFN28 [CX4013]	Z8F0131QJ020SG@QFN28 [CX4013]
Z8F0131SH020EG@SOIC20 [CX1033]	Z8F0131SH020SG@SOIC20 [CX1033]
Z8F0131SJ020EG@SOIC28 [CX1033]	Z8F0131SJ020SG@SOIC28 [CX1033]
Z8F0213HH005EC@SSOP20 [CX1026]	Z8F0213HH005EG@SSOP20 [CX1026]
Z8F0213HH005SC@SSOP20 [CX1026]	Z8F0213HH005SG@SSOP20 [CX1026]
Z8F0213HJ005EC@SSOP28 [CX1026]	Z8F0213HJ005EG@SSOP28 [CX1026]
Z8F0213HJ005SC@SSOP28 [CX1026]	Z8F0213HJ005SG@SSOP28 [CX1026]
Z8F0213PB005EC [CX0001]	Z8F0213PB005EG [CX0001]
Z8F0213PB005SC [CX0001]	Z8F0213PB005SG [CX0001]
Z8F0213PH005EC [CX0001]	Z8F0213PH005EG [CX0001]
Z8F0213PH005SC [CX0001]	Z8F0213PH005SG [CX0001]
Z8F0213PJ005EC [CX0001]	Z8F0213PJ005EG [CX0001]
Z8F0213PJ005SC [CX0001]	Z8F0213PJ005SG [CX0001]
Z8F0213QB005EC@QFN8 [CX4005]	Z8F0213QB005EG@QFN8 [CX4005]
Z8F0213QB005SC@QFN8 [CX4005]	Z8F0213QB005SG@QFN8 [CX4005]
Z8F0213SB005EC@SOIC8 [CX1045]	Z8F0213SB005EG@SOIC8 [CX1045]
Z8F0213SB005SC@SOIC8 [CX1045]	Z8F0213SB005SG@SOIC8 [CX1045]
Z8F0213SH005EC@SOIC20 [CX1033]	Z8F0213SH005EG@SOIC20 [CX1033]
Z8F0213SH005SC@SOIC20 [CX1033]	Z8F0213SH005SG@SOIC20 [CX1033]
Z8F0213SJ005EC@SOIC28 [CX1033]	Z8F0213SJ005EG@SOIC28 [CX1033]
Z8F0213SJ005SC@SOIC28 [CX1033]	Z8F0213SJ005SG@SOIC28 [CX1033]
Z8F021AHH020EC@SSOP20 [CX1026]	Z8F021AHH020EG@SSOP20 [CX1026]
Z8F021AHH020SC@SSOP20 [CX1026]	Z8F021AHH020SG@SSOP20 [CX1026]
Z8F021AHJ020EC@SSOP28 [CX1026]	Z8F021AHJ020EG@SSOP28 [CX1026]
Z8F021AHJ020SC@SSOP28 [CX1026]	Z8F021AHJ020SG@SSOP28 [CX1026]

Z8F021APB020EC [CX0001]	Z8F021APB020EG [CX0001]
Z8F021APB020SC [CX0001]	Z8F021APB020SG [CX0001]
Z8F021APH020EC [CX0001]	Z8F021APH020EG [CX0001]
Z8F021APH020SC [CX0001]	Z8F021APH020SG [CX0001]
Z8F021APJ020EC [CX0001]	Z8F021APJ020EG [CX0001]
Z8F021APJ020SC [CX0001]	Z8F021APJ020SG [CX0001]
Z8F021AQB020EC@QFN8 [CX4005]	Z8F021AQB020EG@QFN8 [CX4005]
Z8F021AQB020SC@QFN8 [CX4005]	Z8F021AQB020SG@QFN8 [CX4005]
Z8F021ASB020EC@SOIC8 [CX1045]	Z8F021ASB020EG@SOIC8 [CX1045]
Z8F021ASB020SC@SOIC8 [CX1045]	Z8F021ASB020SG@SOIC8 [CX1045]
Z8F021ASH020EC@SOIC20 [CX1033]	Z8F021ASH020EG@SOIC20 [CX1033]
Z8F021ASH020SC@SOIC20 [CX1033]	Z8F021ASH020SG@SOIC20 [CX1033]
Z8F021ASJ020EC@SOIC28 [CX1033]	Z8F021ASJ020EG@SOIC28 [CX1033]
Z8F021ASJ020SC@SOIC28 [CX1033]	Z8F021ASJ020SG@SOIC28 [CX1033]
Z8F0223HH005EC@SSOP20 [CX1026]	Z8F0223HH005EG@SSOP20 [CX1026]
Z8F0223HH005SC@SSOP20 [CX1026]	Z8F0223HH005SG@SSOP20 [CX1026]
Z8F0223HJ005EC@SSOP28 [CX1026]	Z8F0223HJ005EG@SSOP28 [CX1026]
Z8F0223HJ005SC@SSOP28 [CX1026]	Z8F0223HJ005SG@SSOP28 [CX1026]
Z8F0223PB005EC [CX0001]	Z8F0223PB005EG [CX0001]
Z8F0223PB005SC [CX0001]	Z8F0223PB005SG [CX0001]
Z8F0223PH005EC [CX0001]	Z8F0223PH005EG [CX0001]
Z8F0223PH005SC [CX0001]	Z8F0223PH005SG [CX0001]
Z8F0223PJ005EC [CX0001]	Z8F0223PJ005EG [CX0001]
Z8F0223PJ005SC [CX0001]	Z8F0223PJ005SG [CX0001]
Z8F0223QB005EC@QFN8 [CX4005]	Z8F0223QB005EG@QFN8 [CX4005]
Z8F0223QB005SC@QFN8 [CX4005]	Z8F0223QB005SG@QFN8 [CX4005]
Z8F0223SB005EC@SOIC8 [CX1045]	Z8F0223SB005EG@SOIC8 [CX1045]
Z8F0223SB005SC@SOIC8 [CX1045]	Z8F0223SB005SG@SOIC8 [CX1045]
Z8F0223SH005EC@SOIC20 [CX1033]	Z8F0223SH005EG@SOIC20 [CX1033]
Z8F0223SH005SC@SOIC20 [CX1033]	Z8F0223SH005SG@SOIC20 [CX1033]
Z8F0223SJ005EC@SOIC28 [CX1033]	Z8F0223SJ005EG@SOIC28 [CX1033]
Z8F0223SJ005SC@SOIC28 [CX1033]	Z8F0223SJ005SG@SOIC28 [CX1033]
Z8F022AHH020EC@SSOP20 [CX1026]	Z8F022AHH020EG@SSOP20 [CX1026]
Z8F022AHH020SC@SSOP20 [CX1026]	Z8F022AHH020SG@SSOP20 [CX1026]
Z8F022AHJ020EC@SSOP28 [CX1026]	Z8F022AHJ020EG@SSOP28 [CX1026]
Z8F022AHJ020SC@SSOP28 [CX1026]	Z8F022AHJ020SG@SSOP28 [CX1026]
Z8F022APB020EC [CX0001]	Z8F022APB020EG [CX0001]
Z8F022APB020SC [CX0001]	Z8F022APB020SG [CX0001]
Z8F022APH020EC [CX0001]	Z8F022APH020EG [CX0001]
Z8F022APH020SC [CX0001]	Z8F022APH020SG [CX0001]
Z8F022APJ020EC [CX0001]	Z8F022APJ020EG [CX0001]
Z8F022APJ020SC [CX0001]	Z8F022APJ020SG [CX0001]
Z8F022AQB020EC@QFN8 [CX4005]	Z8F022AQB020EG@QFN8 [CX4005]
Z8F022AQB020SC@QFN8 [CX4005]	Z8F022AQB020SG@QFN8 [CX4005]
Z8F022ASB020EC@SOIC8 [CX1045]	Z8F022ASB020EG@SOIC8 [CX1045]
Z8F022ASB020SC@SOIC8 [CX1045]	Z8F022ASB020SG@SOIC8 [CX1045]
Z8F022ASH020EC@SOIC20 [CX1033]	Z8F022ASH020EG@SOIC20 [CX1033]
Z8F022ASH020SC@SOIC20 [CX1033]	Z8F022ASH020SG@SOIC20 [CX1033]
Z8F022ASJ020EC@SOIC28 [CX1033]	Z8F022ASJ020EG@SOIC28 [CX1033]
Z8F022ASJ020SC@SOIC28 [CX1033]	Z8F022ASJ020SG@SOIC28 [CX1033]
Z8F0230HH020EG@SSOP20 [CX1026]	Z8F0230HH020SG@SSOP20 [CX1026]
Z8F0230HJ020EG@SSOP28 [CX1026]	Z8F0230HJ020SG@SSOP28 [CX1026]
Z8F0230PH020EG [CX0001]	Z8F0230PH020SG [CX0001]
Z8F0230PJ020EG [CX0001]	Z8F0230PJ020SG [CX0001]
Z8F0230QH020EG@QFN20 [CX4025]	Z8F0230QH020SG@QFN20 [CX4025]
Z8F0230QJ020EG@QFN28 [CX4013]	Z8F0230QJ020SG@QFN28 [CX4013]
Z8F0230SH020EG@SOIC20 [CX1033]	Z8F0230SH020SG@SOIC20 [CX1033]
Z8F0230SJ020EG@SOIC28 [CX1033]	Z8F0230SJ020SG@SOIC28 [CX1033]
Z8F0231HH020EG@SSOP20 [CX1026]	Z8F0231HH020SG@SSOP20 [CX1026]



Z8F0231HJ020EG@SSOP28 [CX1026]  
Z8F0231PH020EG [CX0001]  
Z8F0231PJ020EG [CX0001]  
Z8F0231QH020EG@QFN20 [CX4025]  
Z8F0231QJ020EG@QFN28 [CX4013]  
Z8F0231SH020EG@SOIC20 [CX1033]  
Z8F0231SJ020EG@SOIC28 [CX1033]  
Z8F0411HH020EC@SSOP20 [CX1026]  
Z8F0411HH020SC@SSOP20 [CX1026]  
Z8F0411PH020EC [CX0001]  
Z8F0411PH020SC [CX0001]  
Z8F0412PJ020EC [CX0001]  
Z8F0412PJ020SC [CX0001]  
Z8F0412SJ020EC@SOIC28 [CX1033]  
Z8F0412SJ020SC@SOIC28 [CX1033]  
Z8F0413HH005EC@SSOP20 [CX1026]  
Z8F0413HH005SC@SSOP20 [CX1026]  
Z8F0413HJ005EC@SSOP28 [CX1026]  
Z8F0413HJ005SC@SSOP28 [CX1026]  
Z8F0413PB005EC [CX0001]  
Z8F0413PB005SC [CX0001]  
Z8F0413PH005EC [CX0001]  
Z8F0413PH005SC [CX0001]  
Z8F0413PJ005EC [CX0001]  
Z8F0413PJ005SC [CX0001]  
Z8F0413QB005EC@QFN8 [CX4005]  
Z8F0413QB005SC@QFN8 [CX4005]  
Z8F0413SB005EC@SOIC8 [CX1045]  
Z8F0413SB005SC@SOIC8 [CX1045]  
Z8F0413SH005EC@SOIC20 [CX1033]  
Z8F0413SH005SC@SOIC20 [CX1033]  
Z8F0413SJ005EC@SOIC28 [CX1033]  
Z8F0413SJ005SC@SOIC28 [CX1033]  
Z8F041AHH020EC@SSOP20 [CX1026]  
Z8F041AHH020SC@SSOP20 [CX1026]  
Z8F041AHJ020EC@SSOP28 [CX1026]  
Z8F041AHJ020SC@SSOP28 [CX1026]  
Z8F041APB020EC [CX0001]  
Z8F041APB020SC [CX0001]  
Z8F041APH020EC [CX0001]  
Z8F041APH020SC [CX0001]  
Z8F041APJ020EC [CX0001]  
Z8F041APJ020SC [CX0001]  
Z8F041AQB020EC@QFN8 [CX4005]  
Z8F041AQB020SC@QFN8 [CX4005]  
Z8F041ASB020EC@SOIC8 [CX1045]  
Z8F041ASB020SC@SOIC8 [CX1045]  
Z8F041ASH020EC@SOIC20 [CX1033]  
Z8F041ASH020SC@SOIC20 [CX1033]  
Z8F041ASJ020EC@SOIC28 [CX1033]  
Z8F041ASJ020SC@SOIC28 [CX1033]  
Z8F0421HH020EC@SSOP20 [CX1026]  
Z8F0421HH020SC@SSOP20 [CX1026]  
Z8F0421PH020EC [CX0001]  
Z8F0421PH020SC [CX0001]  
Z8F0422PJ020EC [CX0001]  
Z8F0422PJ020SC [CX0001]  
Z8F0422SJ020EC@SOIC28 [CX1033]  
Z8F0422SJ020SC@SOIC28 [CX1033]

Z8F0231HJ020SG@SSOP28 [CX1026]  
Z8F0231PH020SG [CX0001]  
Z8F0231PJ020SG [CX0001]  
Z8F0231QH020SG@QFN20 [CX4025]  
Z8F0231QJ020SG@QFN28 [CX4013]  
Z8F0231SH020SG@SOIC20 [CX1033]  
Z8F0231SJ020SG@SOIC28 [CX1033]  
Z8F0411HH020EG@SSOP20 [CX1026]  
Z8F0411HH020SG@SSOP20 [CX1026]  
Z8F0411PH020EG [CX0001]  
Z8F0411PH020SG [CX0001]  
Z8F0412PJ020EG [CX0001]  
Z8F0412PJ020SG [CX0001]  
Z8F0412SJ020EG@SOIC28 [CX1033]  
Z8F0412SJ020SG@SOIC28 [CX1033]  
Z8F0413HH005EG@SSOP20 [CX1026]  
Z8F0413HH005SG@SSOP20 [CX1026]  
Z8F0413HJ005EG@SSOP28 [CX1026]  
Z8F0413HJ005SG@SSOP28 [CX1026]  
Z8F0413PB005EG [CX0001]  
Z8F0413PB005SG [CX0001]  
Z8F0413PH005EG [CX0001]  
Z8F0413PH005SG [CX0001]  
Z8F0413PJ005EG [CX0001]  
Z8F0413PJ005SG [CX0001]  
Z8F0413QB005EG@QFN8 [CX4005]  
Z8F0413QB005SG@QFN8 [CX4005]  
Z8F0413SB005EG@SOIC8 [CX1045]  
Z8F0413SB005SG@SOIC8 [CX1045]  
Z8F0413SH005EG@SOIC20 [CX1033]  
Z8F0413SH005SG@SOIC20 [CX1033]  
Z8F0413SJ005EG@SOIC28 [CX1033]  
Z8F0413SJ005SG@SOIC28 [CX1033]  
Z8F041AHH020EG@SSOP20 [CX1026]  
Z8F041AHH020SG@SSOP20 [CX1026]  
Z8F041AHJ020EG@SSOP28 [CX1026]  
Z8F041AHJ020SG@SSOP28 [CX1026]  
Z8F041APB020EG [CX0001]  
Z8F041APB020SG [CX0001]  
Z8F041APH020EG [CX0001]  
Z8F041APH020SG [CX0001]  
Z8F041APJ020EG [CX0001]  
Z8F041APJ020SG [CX0001]  
Z8F041AQB020EG@QFN8 [CX4005]  
Z8F041AQB020SG@QFN8 [CX4005]  
Z8F041ASB020EG@SOIC8 [CX1045]  
Z8F041ASB020SG@SOIC8 [CX1045]  
Z8F041ASH020EG@SOIC20 [CX1033]  
Z8F041ASH020SG@SOIC20 [CX1033]  
Z8F041ASJ020EG@SOIC28 [CX1033]  
Z8F041ASJ020SG@SOIC28 [CX1033]  
Z8F0421HH020EG@SSOP20 [CX1026]  
Z8F0421HH020SG@SSOP20 [CX1026]  
Z8F0421PH020EG [CX0001]  
Z8F0421PH020SG [CX0001]  
Z8F0422PJ020EG [CX0001]  
Z8F0422PJ020SG [CX0001]  
Z8F0422SJ020EG@SOIC28 [CX1033]  
Z8F0422SJ020SG@SOIC28 [CX1033]

Z8F0423HH005EC@SSOP20 [CX1026]  
Z8F0423HH005SC@SSOP20 [CX1026]  
Z8F0423HJ005EC@SSOP28 [CX1026]  
Z8F0423HJ005SC@SSOP28 [CX1026]  
Z8F0423PB005EC [CX0001]  
Z8F0423PB005SC [CX0001]  
Z8F0423PH005EC [CX0001]  
Z8F0423PH005SC [CX0001]  
Z8F0423PJ005EC [CX0001]  
Z8F0423PJ005SC [CX0001]  
Z8F0423QB005EC@QFN8 [CX4005]  
Z8F0423QB005SC@QFN8 [CX4005]  
Z8F0423SB005EC@SOIC8 [CX1045]  
Z8F0423SB005SC@SOIC8 [CX1045]  
Z8F0423SH005EC@SOIC20 [CX1033]  
Z8F0423SH005SC@SOIC20 [CX1033]  
Z8F0423SJ005EC@SOIC28 [CX1033]  
Z8F0423SJ005SC@SOIC28 [CX1033]  
Z8F0423AHH020EC@SSOP20 [CX1026]  
Z8F0423AHH020SC@SSOP20 [CX1026]  
Z8F0423AHJ020EC@SSOP28 [CX1026]  
Z8F0423AHJ020SC@SSOP28 [CX1026]  
Z8F0423APB020EC [CX0001]  
Z8F0423APB020SC [CX0001]  
Z8F0423APH020EC [CX0001]  
Z8F0423APH020SC [CX0001]  
Z8F0423APJ020EC [CX0001]  
Z8F0423APJ020SC [CX0001]  
Z8F0423AQB020EC@QFN8 [CX4005]  
Z8F0423AQB020SC@QFN8 [CX4005]  
Z8F0423ASB020EC@SOIC8 [CX1045]  
Z8F0423ASB020SC@SOIC8 [CX1045]  
Z8F0423ASH020EC@SOIC20 [CX1033]  
Z8F0423ASH020SC@SOIC20 [CX1033]  
Z8F0423ASJ020EC@SOIC28 [CX1033]  
Z8F0423ASJ020SC@SOIC28 [CX1033]  
Z8F0430HH020EG@SSOP20 [CX1026]  
Z8F0430HJ020EG@SSOP28 [CX1026]  
Z8F0430PH020EG [CX0001]  
Z8F0430PJ020EG [CX0001]  
Z8F0430QH020EG@QFN20 [CX4025]  
Z8F0430QJ020EG@QFN28 [CX4013]  
Z8F0430SH020EG@SOIC20 [CX1033]  
Z8F0430SJ020EG@SOIC28 [CX1033]  
Z8F0431HH020EG@SSOP20 [CX1026]  
Z8F0431HJ020EG@SSOP28 [CX1026]  
Z8F0431PH020EG [CX0001]  
Z8F0431PJ020EG [CX0001]  
Z8F0431QH020EG@QFN20 [CX4025]  
Z8F0431QJ020EG@QFN28 [CX4013]  
Z8F0431SH020EG@SOIC20 [CX1033]  
Z8F0431SJ020EG@SOIC28 [CX1033]  
Z8F0431AHH020EG@SSOP20 [CX1026]  
Z8F0431AHJ020EG@SSOP28 [CX1026]  
Z8F0431APH020EG [CX0001]  
Z8F0431APJ020EG [CX0001]  
Z8F0431AQH020EG@QFN20 [CX4025]  
Z8F0431AQJ020EG@QFN28 [CX4013]  
Z8F0431ASH020EG@SOIC20 [CX1033]

Z8F0423HH005EG@SSOP20 [CX1026]  
Z8F0423HH005SG@SSOP20 [CX1026]  
Z8F0423HJ005EG@SSOP28 [CX1026]  
Z8F0423HJ005SG@SSOP28 [CX1026]  
Z8F0423PB005EG [CX0001]  
Z8F0423PB005SG [CX0001]  
Z8F0423PH005EG [CX0001]  
Z8F0423PH005SG [CX0001]  
Z8F0423PJ005EG [CX0001]  
Z8F0423PJ005SG [CX0001]  
Z8F0423QB005EG@QFN8 [CX4005]  
Z8F0423QB005SG@QFN8 [CX4005]  
Z8F0423SB005EG@SOIC8 [CX1045]  
Z8F0423SB005SG@SOIC8 [CX1045]  
Z8F0423SH005EG@SOIC20 [CX1033]  
Z8F0423SH005SG@SOIC20 [CX1033]  
Z8F0423SJ005EG@SOIC28 [CX1033]  
Z8F0423SJ005SG@SOIC28 [CX1033]  
Z8F0423AHH020EG@SSOP20 [CX1026]  
Z8F0423AHH020SG@SSOP20 [CX1026]  
Z8F0423AHJ020EG@SSOP28 [CX1026]  
Z8F0423AHJ020SG@SSOP28 [CX1026]  
Z8F0423APB020EG [CX0001]  
Z8F0423APB020SG [CX0001]  
Z8F0423APH020EG [CX0001]  
Z8F0423APH020SG [CX0001]  
Z8F0423APJ020EG [CX0001]  
Z8F0423APJ020SG [CX0001]  
Z8F0423AQB020EG@QFN8 [CX4005]  
Z8F0423AQB020SG@QFN8 [CX4005]  
Z8F0423ASB020EG@SOIC8 [CX1045]  
Z8F0423ASB020SG@SOIC8 [CX1045]  
Z8F0423ASH020EG@SOIC20 [CX1033]  
Z8F0423ASH020SG@SOIC20 [CX1033]  
Z8F0423ASJ020EG@SOIC28 [CX1033]  
Z8F0423ASJ020SG@SOIC28 [CX1033]  
Z8F0430HH020SG@SSOP20 [CX1026]  
Z8F0430HJ020SG@SSOP28 [CX1026]  
Z8F0430PH020SG [CX0001]  
Z8F0430PJ020SG [CX0001]  
Z8F0430QH020SG@QFN20 [CX4025]  
Z8F0430QJ020SG@QFN28 [CX4013]  
Z8F0430SH020SG@SOIC20 [CX1033]  
Z8F0430SJ020SG@SOIC28 [CX1033]  
Z8F0431HH020SG@SSOP20 [CX1026]  
Z8F0431HJ020SG@SSOP28 [CX1026]  
Z8F0431PH020SG [CX0001]  
Z8F0431PJ020SG [CX0001]  
Z8F0431QH020SG@QFN20 [CX4025]  
Z8F0431QJ020SG@QFN28 [CX4013]  
Z8F0431SH020SG@SOIC20 [CX1033]  
Z8F0431SJ020SG@SOIC28 [CX1033]  
Z8F0431AHH020SG@SSOP20 [CX1026]  
Z8F0431AHJ020SG@SSOP28 [CX1026]  
Z8F0431APH020SG [CX0001]  
Z8F0431APJ020SG [CX0001]  
Z8F0431AQH020SG@QFN20 [CX4025]  
Z8F0431AQJ020SG@QFN28 [CX4013]  
Z8F0431ASH020SG@SOIC20 [CX1033]

Z8F043ASJ020EG@SOIC28 [CX1033]	Z8F043ASJ020SG@SOIC28 [CX1033]
Z8F0811HH020EC@SSOP20 [CX1026]	Z8F0811HH020EG@SSOP20 [CX1026]
Z8F0811HH020SC@SSOP20 [CX1026]	Z8F0811HH020SG@SSOP20 [CX1026]
Z8F0811PH020EC [CX0001]	Z8F0811PH020EG [CX0001]
Z8F0811PH020SC [CX0001]	Z8F0811PH020SG [CX0001]
Z8F0812PJ020EC [CX0001]	Z8F0812PJ020EG [CX0001]
Z8F0812PJ020SC [CX0001]	Z8F0812PJ020SG [CX0001]
Z8F0812SJ020EC@SOIC28 [CX1033]	Z8F0812SJ020EG@SOIC28 [CX1033]
Z8F0812SJ020SC@SOIC28 [CX1033]	Z8F0812SJ020SG@SOIC28 [CX1033]
Z8F0813HH005EC@SSOP20 [CX1026]	Z8F0813HH005EG@SSOP20 [CX1026]
Z8F0813HH005SC@SSOP20 [CX1026]	Z8F0813HH005SG@SSOP20 [CX1026]
Z8F0813HJ020EC@SSOP28 [CX1026]	Z8F0813HJ020EG@SSOP28 [CX1026]
Z8F0813HJ020SC@SSOP28 [CX1026]	Z8F0813HJ020SG@SSOP28 [CX1026]
Z8F0813PB005EC [CX0001]	Z8F0813PB005EG [CX0001]
Z8F0813PB005SC [CX0001]	Z8F0813PB005SG [CX0001]
Z8F0813PH005EC [CX0001]	Z8F0813PH005EG [CX0001]
Z8F0813PH005SC [CX0001]	Z8F0813PH005SG [CX0001]
Z8F0813PJ020EC [CX0001]	Z8F0813PJ020EG [CX0001]
Z8F0813PJ020SC [CX0001]	Z8F0813PJ020SG [CX0001]
Z8F0813QB005EC@QFN8 [CX4005]	Z8F0813QB005EG@QFN8 [CX4005]
Z8F0813QB005SC@QFN8 [CX4005]	Z8F0813QB005SG@QFN8 [CX4005]
Z8F0813SB005EC@SOIC8 [CX1045]	Z8F0813SB005EG@SOIC8 [CX1045]
Z8F0813SB005SC@SOIC8 [CX1045]	Z8F0813SB005SG@SOIC8 [CX1045]
Z8F0813SH005EC@SOIC20 [CX1033]	Z8F0813SH005EG@SOIC20 [CX1033]
Z8F0813SH005SC@SOIC20 [CX1033]	Z8F0813SH005SG@SOIC20 [CX1033]
Z8F0813SJ020EC@SOIC28 [CX1033]	Z8F0813SJ020EG@SOIC28 [CX1033]
Z8F0813SJ020SC@SOIC28 [CX1033]	Z8F0813SJ020SG@SOIC28 [CX1033]
Z8F081AHH005EC@SSOP20 [CX1026]	Z8F081AHH005EG@SSOP20 [CX1026]
Z8F081AHH005SC@SSOP20 [CX1026]	Z8F081AHH005SG@SSOP20 [CX1026]
Z8F081AHJ020EC@SSOP28 [CX1026]	Z8F081AHJ020EG@SSOP28 [CX1026]
Z8F081AHJ020SC@SSOP28 [CX1026]	Z8F081AHJ020SG@SSOP28 [CX1026]
Z8F081APB020EC [CX0001]	Z8F081APB020EG [CX0001]
Z8F081APB020SC [CX0001]	Z8F081APB020SG [CX0001]
Z8F081APH005EC [CX0001]	Z8F081APH005EG [CX0001]
Z8F081APH005SC [CX0001]	Z8F081APH005SG [CX0001]
Z8F081APJ020EC [CX0001]	Z8F081APJ020EG [CX0001]
Z8F081APJ020SC [CX0001]	Z8F081APJ020SG [CX0001]
Z8F081AQB020EC@QFN8 [CX4005]	Z8F081AQB020EG@QFN8 [CX4005]
Z8F081AQB020SC@QFN8 [CX4005]	Z8F081AQB020SG@QFN8 [CX4005]
Z8F081ASB020EC@SOIC8 [CX1045]	Z8F081ASB020EG@SOIC8 [CX1045]
Z8F081ASB020SC@SOIC8 [CX1045]	Z8F081ASB020SG@SOIC8 [CX1045]
Z8F081ASH005EC@SOIC20 [CX1033]	Z8F081ASH005EG@SOIC20 [CX1033]
Z8F081ASH005SC@SOIC20 [CX1033]	Z8F081ASH005SG@SOIC20 [CX1033]
Z8F081ASJ020EC@SOIC28 [CX1033]	Z8F081ASJ020EG@SOIC28 [CX1033]
Z8F081ASJ020SC@SOIC28 [CX1033]	Z8F081ASJ020SG@SOIC28 [CX1033]
Z8F0821HH020EC@SSOP20 [CX1026]	Z8F0821HH020EG@SSOP20 [CX1026]
Z8F0821HH020SC@SSOP20 [CX1026]	Z8F0821HH020SG@SSOP20 [CX1026]
Z8F0821PH020EC [CX0001]	Z8F0821PH020EG [CX0001]
Z8F0821PH020SC [CX0001]	Z8F0821PH020SG [CX0001]
Z8F0822PJ020EC [CX0001]	Z8F0822PJ020EG [CX0001]
Z8F0822PJ020SC [CX0001]	Z8F0822PJ020SG [CX0001]
Z8F0822SJ020EC@SOIC28 [CX1033]	Z8F0822SJ020EG@SOIC28 [CX1033]
Z8F0822SJ020SC@SOIC28 [CX1033]	Z8F0822SJ020SG@SOIC28 [CX1033]
Z8F0823HH005EC@SSOP20 [CX1026]	Z8F0823HH005EG@SSOP20 [CX1026]
Z8F0823HH005SC@SSOP20 [CX1026]	Z8F0823HH005SG@SSOP20 [CX1026]
Z8F0823HJ020EC@SSOP28 [CX1026]	Z8F0823HJ020EG@SSOP28 [CX1026]
Z8F0823HJ020SC@SSOP28 [CX1026]	Z8F0823HJ020SG@SSOP28 [CX1026]
Z8F0823PB005EC [CX0001]	Z8F0823PB005EG [CX0001]
Z8F0823PB005SC [CX0001]	Z8F0823PB005SG [CX0001]

Z8F0823PH005EC [CX0001]	Z8F0823PH005EG [CX0001]
Z8F0823PH005SC [CX0001]	Z8F0823PH005SG [CX0001]
Z8F0823PJ020EC [CX0001]	Z8F0823PJ020EG [CX0001]
Z8F0823PJ020SC [CX0001]	Z8F0823PJ020SG [CX0001]
Z8F0823QB005EC@QFN8 [CX4005]	Z8F0823QB005EG@QFN8 [CX4005]
Z8F0823QB005SC@QFN8 [CX4005]	Z8F0823QB005SG@QFN8 [CX4005]
Z8F0823SB005EC@SOIC8 [CX1045]	Z8F0823SB005EG@SOIC8 [CX1045]
Z8F0823SB005SC@SOIC8 [CX1045]	Z8F0823SB005SG@SOIC8 [CX1045]
Z8F0823SH005EC@SOIC20 [CX1033]	Z8F0823SH005EG@SOIC20 [CX1033]
Z8F0823SH005SC@SOIC20 [CX1033]	Z8F0823SH005SG@SOIC20 [CX1033]
Z8F0823SJ020EC@SOIC28 [CX1033]	Z8F0823SJ020EG@SOIC28 [CX1033]
Z8F0823SJ020SC@SOIC28 [CX1033]	Z8F0823SJ020SG@SOIC28 [CX1033]
Z8F0823AHH005EC@SSOP20 [CX1026]	Z8F0823AHH005EG@SSOP20 [CX1026]
Z8F0823AHH005SC@SSOP20 [CX1026]	Z8F0823AHH005SG@SSOP20 [CX1026]
Z8F0823AHJ020EC@SSOP28 [CX1026]	Z8F0823AHJ020EG@SSOP28 [CX1026]
Z8F0823AHJ020SC@SSOP28 [CX1026]	Z8F0823AHJ020SG@SSOP28 [CX1026]
Z8F0823APB020EC [CX0001]	Z8F0823APB020EG [CX0001]
Z8F0823APB020SC [CX0001]	Z8F0823APB020SG [CX0001]
Z8F0823APH005EC [CX0001]	Z8F0823APH005EG [CX0001]
Z8F0823APH005SC [CX0001]	Z8F0823APH005SG [CX0001]
Z8F0823APJ020EC [CX0001]	Z8F0823APJ020EG [CX0001]
Z8F0823APJ020SC [CX0001]	Z8F0823APJ020SG [CX0001]
Z8F0823AQB020EC@QFN8 [CX4005]	Z8F0823AQB020EG@QFN8 [CX4005]
Z8F0823AQB020SC@QFN8 [CX4005]	Z8F0823AQB020SG@QFN8 [CX4005]
Z8F0823ASB020EC@SOIC8 [CX1045]	Z8F0823ASB020EG@SOIC8 [CX1045]
Z8F0823ASB020SC@SOIC8 [CX1045]	Z8F0823ASB020SG@SOIC8 [CX1045]
Z8F0823ASH005EC@SOIC20 [CX1033]	Z8F0823ASH005EG@SOIC20 [CX1033]
Z8F0823ASH005SC@SOIC20 [CX1033]	Z8F0823ASH005SG@SOIC20 [CX1033]
Z8F0823ASJ020EC@SOIC28 [CX1033]	Z8F0823ASJ020EG@SOIC28 [CX1033]
Z8F0823ASJ020SC@SOIC28 [CX1033]	Z8F0823ASJ020SG@SOIC28 [CX1033]
Z8F0830HH020EG@SSOP20 [CX1026]	Z8F0830HH020SG@SSOP20 [CX1026]
Z8F0830HJ020EG@SSOP28 [CX1026]	Z8F0830HJ020SG@SSOP28 [CX1026]
Z8F0830PH020EG [CX0001]	Z8F0830PH020SG [CX0001]
Z8F0830PJ020EG [CX0001]	Z8F0830PJ020SG [CX0001]
Z8F0830QH020EG@QFN20 [CX4025]	Z8F0830QH020SG@QFN20 [CX4025]
Z8F0830QJ020EG@QFN28 [CX4013]	Z8F0830QJ020SG@QFN28 [CX4013]
Z8F0830SH020EG@SOIC20 [CX1033]	Z8F0830SH020SG@SOIC20 [CX1033]
Z8F0830SJ020EG@SOIC28 [CX1033]	Z8F0830SJ020SG@SOIC28 [CX1033]
Z8F0831HH020EG@SSOP20 [CX1026]	Z8F0831HH020SG@SSOP20 [CX1026]
Z8F0831HJ020EG@SSOP28 [CX1026]	Z8F0831HJ020SG@SSOP28 [CX1026]
Z8F0831PH020EG [CX0001]	Z8F0831PH020SG [CX0001]
Z8F0831PJ020EG [CX0001]	Z8F0831PJ020SG [CX0001]
Z8F0831QH020EG@QFN20 [CX4025]	Z8F0831QH020SG@QFN20 [CX4025]
Z8F0831QJ020EG@QFN28 [CX4013]	Z8F0831QJ020SG@QFN28 [CX4013]
Z8F0831SH020EG@SOIC20 [CX1033]	Z8F0831SH020SG@SOIC20 [CX1033]
Z8F0831SJ020EG@SOIC28 [CX1033]	Z8F0831SJ020SG@SOIC28 [CX1033]
Z8F0831AHH020EG@SSOP20 [CX1026]	Z8F0831AHH020SG@SSOP20 [CX1026]
Z8F0831AHJ020EG@SSOP28 [CX1026]	Z8F0831AHJ020SG@SSOP28 [CX1026]
Z8F0831APH020EG [CX0001]	Z8F0831APH020SG [CX0001]
Z8F0831APJ020EG [CX0001]	Z8F0831APJ020SG [CX0001]
Z8F0831AQH020EG@QFN20 [CX4025]	Z8F0831AQH020SG@QFN20 [CX4025]
Z8F0831AQJ020EG@QFN28 [CX4013]	Z8F0831AQJ020SG@QFN28 [CX4013]
Z8F0831ASH020EG@SOIC20 [CX1033]	Z8F0831ASH020SG@SOIC20 [CX1033]
Z8F0831ASJ020EG@SOIC28 [CX1033]	Z8F0831ASJ020SG@SOIC28 [CX1033]
Z8F0880AN020EG@QFP44 [CX3005]	Z8F0880AN020SG@QFP44 [CX3005]
Z8F0880HH020EG@SSOP20 [CX1026]	Z8F0880HH020SG@SSOP20 [CX1026]
Z8F0880HJ020EG@SSOP28 [CX1026]	Z8F0880HJ020SG@SSOP28 [CX1026]
Z8F0880PH020EG [CX0001]	Z8F0880PH020SG [CX0001]
Z8F0880PJ020EG [CX0001]	Z8F0880PJ020SG [CX0001]

Z8F0880PM020EG [CX0001]  
Z8F0880QN020EG@QFN44 [CX4018]  
Z8F0880SH020EG@SOIC20 [CX1033]  
Z8F0880SJ020EG@SOIC28 [CX1033]  
Z8F1232HH020EG@SSOP20 [CX1026]  
Z8F1232HJ020EG@SSOP28 [CX1026]  
Z8F1232PH020EG [CX0001]  
Z8F1232PJ020EG [CX0001]  
Z8F1232QH020EG@QFN20 [CX4025]  
Z8F1232QJ020EG@QFN28 [CX4013]  
Z8F1232SH020EG@SOIC20 [CX1033]  
Z8F1232SJ020EG@SOIC28 [CX1033]  
Z8F1233HH020EG@SSOP20 [CX1026]  
Z8F1233HJ020EG@SSOP28 [CX1026]  
Z8F1233PH020EG [CX0001]  
Z8F1233PJ020EG [CX0001]  
Z8F1233QH020EG@QFN20 [CX4025]  
Z8F1233QJ020EG@QFN28 [CX4013]  
Z8F1233SH020EG@SOIC20 [CX1033]  
Z8F1233SJ020EG@SOIC28 [CX1033]  
Z8F1601AN020EC@LQFP44 [CX3005]  
Z8F1601AN020SC@LQFP44 [CX3005]  
Z8F1601PM020EC [CX0001]  
Z8F1601PM020SC [CX0001]  
Z8F1601VN020EC@PLCC44 [CX2044]  
Z8F1601VN020SC@PLCC44 [CX2044]  
Z8F1602AN020EC@LQFP44 [CX3005]  
Z8F1602AN020SC@LQFP44 [CX3005]  
Z8F1602PM020EC [CX0001]  
Z8F1602PM020SC [CX0001]  
Z8F1602VN020EC@PLCC44 [CX2044]  
Z8F1602VN020SC@PLCC44 [CX2044]  
Z8F1621AN020AC@LQFP44 [CX3005]  
Z8F1621AN020EC@LQFP44 [CX3005]  
Z8F1621AN020SC@LQFP44 [CX3005]  
Z8F1621PM020AC [CX0001]  
Z8F1621PM020EC [CX0001]  
Z8F1621PM020SC [CX0001]  
Z8F1621VN020AC@PLCC44 [CX2044]  
Z8F1621VN020EC@PLCC44 [CX2044]  
Z8F1621VN020SC@PLCC44 [CX2044]  
Z8F1622AR020AC@LQFP64 [CX3011]  
Z8F1622AR020EC@LQFP64 [CX3011]  
Z8F1622AR020SC@LQFP64 [CX3011]  
Z8F1622VS020AC@PLCC68 [CX2068]  
Z8F1622VS020EC@PLCC68 [CX2068]  
Z8F1622VS020SC@PLCC68 [CX2068]  
Z8F1680AN020EG@QFP44 [CX3005]  
Z8F1680HH020EG@SSOP20 [CX1026]  
Z8F1680HJ020EG@SSOP28 [CX1026]  
Z8F1680PH020EG [CX0001]  
Z8F1680PJ020EG [CX0001]  
Z8F1680PM020EG [CX0001]  
Z8F1680QN020EG@QFN44 [CX4018]  
Z8F1680SH020EG@SOIC20 [CX1033]  
Z8F1680SJ020EG@SOIC28 [CX1033]  
Z8F2421AN020AC@LQFP44 [CX3005]  
Z8F2421AN020EC@LQFP44 [CX3005]  
Z8F2421AN020SC@LQFP44 [CX3005]

Z8F0880PM020SG [CX0001]  
Z8F0880QN020SG@QFN44 [CX4018]  
Z8F0880SH020SG@SOIC20 [CX1033]  
Z8F0880SJ020SG@SOIC28 [CX1033]  
Z8F1232HH020SG@SSOP20 [CX1026]  
Z8F1232HJ020SG@SSOP28 [CX1026]  
Z8F1232PH020SG [CX0001]  
Z8F1232PJ020SG [CX0001]  
Z8F1232QH020SG@QFN20 [CX4025]  
Z8F1232QJ020SG@QFN28 [CX4013]  
Z8F1232SH020SG@SOIC20 [CX1033]  
Z8F1232SJ020SG@SOIC28 [CX1033]  
Z8F1233HH020SG@SSOP20 [CX1026]  
Z8F1233HJ020SG@SSOP28 [CX1026]  
Z8F1233PH020SG [CX0001]  
Z8F1233PJ020SG [CX0001]  
Z8F1233QH020SG@QFN20 [CX4025]  
Z8F1233QJ020SG@QFN28 [CX4013]  
Z8F1233SH020SG@SOIC20 [CX1033]  
Z8F1233SJ020SG@SOIC28 [CX1033]  
Z8F1601AN020EG@LQFP44 [CX3005]  
Z8F1601AN020SG@LQFP44 [CX3005]  
Z8F1601PM020EG [CX0001]  
Z8F1601PM020SG [CX0001]  
Z8F1601VN020EG@PLCC44 [CX2044]  
Z8F1601VN020SG@PLCC44 [CX2044]  
Z8F1602AN020EG@LQFP44 [CX3005]  
Z8F1602AN020SG@LQFP44 [CX3005]  
Z8F1602PM020EG [CX0001]  
Z8F1602PM020SG [CX0001]  
Z8F1602VN020EG@PLCC44 [CX2044]  
Z8F1602VN020SG@PLCC44 [CX2044]  
Z8F1621AN020AG@LQFP44 [CX3005]  
Z8F1621AN020EG@LQFP44 [CX3005]  
Z8F1621AN020SG@LQFP44 [CX3005]  
Z8F1621PM020AG [CX0001]  
Z8F1621PM020EG [CX0001]  
Z8F1621PM020SG [CX0001]  
Z8F1621VN020AG@PLCC44 [CX2044]  
Z8F1621VN020EG@PLCC44 [CX2044]  
Z8F1621VN020SG@PLCC44 [CX2044]  
Z8F1622AR020AG@LQFP64 [CX3011]  
Z8F1622AR020EG@LQFP64 [CX3011]  
Z8F1622AR020SG@LQFP64 [CX3011]  
Z8F1622VS020AG@PLCC68 [CX2068]  
Z8F1622VS020EG@PLCC68 [CX2068]  
Z8F1622VS020SG@PLCC68 [CX2068]  
Z8F1680AN020SG@QFP44 [CX3005]  
Z8F1680HH020SG@SSOP20 [CX1026]  
Z8F1680HJ020SG@SSOP28 [CX1026]  
Z8F1680PH020SG [CX0001]  
Z8F1680PJ020SG [CX0001]  
Z8F1680PM020SG [CX0001]  
Z8F1680QN020SG@QFN44 [CX4018]  
Z8F1680SH020SG@SOIC20 [CX1033]  
Z8F1680SJ020SG@SOIC28 [CX1033]  
Z8F2421AN020AG@LQFP44 [CX3005]  
Z8F2421AN020EG@LQFP44 [CX3005]  
Z8F2421AN020SG@LQFP44 [CX3005]

Z8F2421PM020AC [CX0001]  
Z8F2421PM020EC [CX0001]  
Z8F2421PM020SC [CX0001]  
Z8F2421VN020AC@PLCC44 [CX2044]  
Z8F2421VN020EC@PLCC44 [CX2044]  
Z8F2421VN020SC@PLCC44 [CX2044]  
Z8F2422AR020AC@LQFP64 [CX3011]  
Z8F2422AR020EC@LQFP64 [CX3011]  
Z8F2422AR020SC@LQFP64 [CX3011]  
Z8F2422VS020AC@PLCC68 [CX2068]  
Z8F2422VS020EC@PLCC68 [CX2068]  
Z8F2422VS020SC@PLCC68 [CX2068]  
Z8F2480AN020EG@QFP44 [CX3005]  
Z8F2480HH020EG@SSOP20 [CX1026]  
Z8F2480HJ020EG@SSOP28 [CX1026]  
Z8F2480PH020EG [CX0001]  
Z8F2480PJ020EG [CX0001]  
Z8F2480PM020EG [CX0001]  
Z8F2480QN020EG@QFN44 [CX4018]  
Z8F2480SH020EG@SOIC20 [CX1033]  
Z8F2480SJ020EG@SOIC28 [CX1033]  
Z8F3221AN020AC@LQFP44 [CX3005]  
Z8F3221AN020EC@LQFP44 [CX3005]  
Z8F3221AN020SC@LQFP44 [CX3005]  
Z8F3221PM020AC [CX0001]  
Z8F3221PM020EC [CX0001]  
Z8F3221PM020SC [CX0001]  
Z8F3221VN020AC@PLCC44 [CX2044]  
Z8F3221VN020EC@PLCC44 [CX2044]  
Z8F3221VN020SC@PLCC44 [CX2044]  
Z8F3222AR020AC@LQFP64 [CX3011]  
Z8F3222AR020EC@LQFP64 [CX3011]  
Z8F3222AR020SC@LQFP64 [CX3011]  
Z8F3222VS020AC@PLCC68 [CX2068]  
Z8F3222VS020EC@PLCC68 [CX2068]  
Z8F3222VS020SC@PLCC68 [CX2068]  
Z8F3280AN020EG@QFP44 [CX3005]  
Z8F3280HH020EG@SSOP20 [CX1026]  
Z8F3280HJ020EG@SSOP28 [CX1026]  
Z8F3280PH020EG [CX0001]  
Z8F3280PJ020EG [CX0001]  
Z8F3280PM020EG [CX0001]  
Z8F3280QN020EG@QFN44 [CX4018]  
Z8F3280SH020EG@SOIC20 [CX1033]  
Z8F3280SJ020EG@SOIC28 [CX1033]  
Z8F4801AN@TQFP44 [CX3005]  
Z8F4801VN@PLCC44 [CX2044]  
Z8F4821AN020AC@LQFP44 [CX3005]  
Z8F4821AN020EC@LQFP44 [CX3005]  
Z8F4821AN020EG21@LQFP44 [CX3005]  
Z8F4821AN020SG@LQFP44 [CX3005]  
Z8F4821PM020AC [CX0001]  
Z8F4821PM020EC [CX0001]  
Z8F4821PM020SC [CX0001]  
Z8F4821VN020AC@PLCC44 [CX2044]  
Z8F4821VN020EC@PLCC44 [CX2044]  
Z8F4821VN020SC@PLCC44 [CX2044]  
Z8F4822AR020AC@LQFP64 [CX3011]  
Z8F4822AR020EC@LQFP64 [CX3011]

Z8F2421PM020AG [CX0001]  
Z8F2421PM020EG [CX0001]  
Z8F2421PM020SG [CX0001]  
Z8F2421VN020AG@PLCC44 [CX2044]  
Z8F2421VN020EG@PLCC44 [CX2044]  
Z8F2421VN020SG@PLCC44 [CX2044]  
Z8F2422AR020AG@LQFP64 [CX3011]  
Z8F2422AR020EG@LQFP64 [CX3011]  
Z8F2422AR020SG@LQFP64 [CX3011]  
Z8F2422VS020AG@PLCC68 [CX2068]  
Z8F2422VS020EG@PLCC68 [CX2068]  
Z8F2422VS020SG@PLCC68 [CX2068]  
Z8F2480AN020SG@QFP44 [CX3005]  
Z8F2480HH020SG@SSOP20 [CX1026]  
Z8F2480HJ020SG@SSOP28 [CX1026]  
Z8F2480PH020SG [CX0001]  
Z8F2480PJ020SG [CX0001]  
Z8F2480PM020SG [CX0001]  
Z8F2480QN020SG@QFN44 [CX4018]  
Z8F2480SH020SG@SOIC20 [CX1033]  
Z8F2480SJ020SG@SOIC28 [CX1033]  
Z8F3221AN020AG@LQFP44 [CX3005]  
Z8F3221AN020EG@LQFP44 [CX3005]  
Z8F3221AN020SG@LQFP44 [CX3005]  
Z8F3221PM020AG [CX0001]  
Z8F3221PM020EG [CX0001]  
Z8F3221PM020SG [CX0001]  
Z8F3221VN020AG@PLCC44 [CX2044]  
Z8F3221VN020EG@PLCC44 [CX2044]  
Z8F3221VN020SG@PLCC44 [CX2044]  
Z8F3222AR020AG@LQFP64 [CX3011]  
Z8F3222AR020EG@LQFP64 [CX3011]  
Z8F3222AR020SG@LQFP64 [CX3011]  
Z8F3222VS020AG@PLCC68 [CX2068]  
Z8F3222VS020EG@PLCC68 [CX2068]  
Z8F3222VS020SG@PLCC68 [CX2068]  
Z8F3280AN020SG@QFP44 [CX3005]  
Z8F3280HH020SG@SSOP20 [CX1026]  
Z8F3280HJ020SG@SSOP28 [CX1026]  
Z8F3280PH020SG [CX0001]  
Z8F3280PJ020SG [CX0001]  
Z8F3280PM020SG [CX0001]  
Z8F3280QN020SG@QFN44 [CX4018]  
Z8F3280SH020SG@SOIC20 [CX1033]  
Z8F3280SJ020SG@SOIC28 [CX1033]  
Z8F4801PM [CX0001]  
Z8F4802AR020SC@LQFP64 [CX3011]  
Z8F4821AN020AG@LQFP44 [CX3005]  
Z8F4821AN020EG@LQFP44 [CX3005]  
Z8F4821AN020SC@LQFP44 [CX3005]  
Z8F4821AN020SG21@LQFP44 [CX3005]  
Z8F4821PM020AG [CX0001]  
Z8F4821PM020EG [CX0001]  
Z8F4821PM020SG [CX0001]  
Z8F4821VN020AG@PLCC44 [CX2044]  
Z8F4821VN020EG@PLCC44 [CX2044]  
Z8F4821VN020SG@PLCC44 [CX2044]  
Z8F4822AR020AG@LQFP64 [CX3011]  
Z8F4822AR020EG@LQFP64 [CX3011]

Z8F4822AR020SC@LQFP64 [CX3011]  
Z8F4822VS020AC@PLCC68 [CX2068]  
Z8F4822VS020EC@PLCC68 [CX2068]  
Z8F4822VS020SC@PLCC68 [CX2068]  
Z8F4823FT020AC@QFP80 [CX3019]  
Z8F4823FT020EC@QFP80 [CX3019]  
Z8F4823FT020SC@QFP80 [CX3019]  
Z8F6401AN@TQFP44 [CX3005]  
Z8F6401VN@PLCC44 [CX2044]  
Z8F6402AR020SC@LQFP64 [CX3011]  
Z8F6402VS020SC@PLCC68 [CX2068]  
Z8F6403FT020SC@QFP80 [CX3019]  
Z8F6421AN020AG@LQFP44 [CX3005]  
Z8F6421AN020EG@LQFP44 [CX3005]  
Z8F6421AN020SG@LQFP44 [CX3005]  
Z8F6421PM020AG [CX0001]  
Z8F6421PM020EG [CX0001]  
Z8F6421PM020SG [CX0001]  
Z8F6421VN020AG@PLCC44  
Z8F6421VN020EG@PLCC44  
Z8F6421VN020SG@PLCC44  
Z8F6422AR020AG@LQFP64 [CX3011]  
Z8F6422AR020EG@LQFP64 [CX3011]  
Z8F6422AR020SG@LQFP64 [CX3011]  
Z8F6422VS020AG@PLCC68 [CX2068]  
Z8F6422VS020EG@PLCC68 [CX2068]  
Z8F6422VS020SG@PLCC68 [CX2068]  
Z8F6423FT020AG@QFP80 [CX3019]  
Z8F6423FT020EG@QFP80 [CX3019]  
Z8F6423FT020SG@QFP80 [CX3019]  
Z8FMC04100AKEG@QFP32 [CX3001]  
Z8FMC04100AKSG@QFP32 [CX3001]  
Z8FMC04100QKEG@QFN32 [CX4015]  
Z8FMC04100QKSG@QFN32 [CX4015]  
Z8FMC08100AKEG@QFP32 [CX3001]  
Z8FMC08100AKSG@QFP32 [CX3001]  
Z8FMC08100QKEG@QFN32 [CX4015]  
Z8FMC08100QKSG@QFN32 [CX4015]  
Z8FMC16100AKEG@QFP32 [CX3001]  
Z8FMC16100AKSG@QFP32 [CX3001]  
Z8FMC16100QKEG@QFN32 [CX4015]  
Z8FMC16100QKSG@QFN32 [CX4015]  
Z8FMC32100AKEG@QFP32 [CX3001]  
Z8FMC32100AKSG@QFP32 [CX3001]  
Z8FMC32100QKEG@QFN32 [CX4015]  
Z8FMC32100QKSG@QFN32 [CX4015]  
Z8FMC64100AKEG@QFP32 [CX3001]  
Z8FMC64100AKSG@QFP32 [CX3001]  
Z8FMC64100QKEG@QFN32 [CX4015]  
Z8FMC64100QKSG@QFN32 [CX4015]  
Z8FS011APB020EG [CX0001]  
Z8FS011APB020SG [CX0001]  
Z8FS011AQB020EG [CX4005]  
Z8FS011AQB020SG [CX4005]  
Z8FS011ASB020EG [CX1045]  
Z8FS011ASB020SG [CX1045]  
Z8FS012APB020EG [CX0001]  
Z8FS012APB020SG [CX0001]  
Z8FS012AQB020EG [CX4005]

Z8F4822AR020SG@LQFP64 [CX3011]  
Z8F4822VS020AG@PLCC68 [CX2068]  
Z8F4822VS020EG@PLCC68 [CX2068]  
Z8F4822VS020SG@PLCC68 [CX2068]  
Z8F4823FT020AG@QFP80 [CX3019]  
Z8F4823FT020EG@QFP80 [CX3019]  
Z8F4823FT020SG@QFP80 [CX3019]  
Z8F6401PM [CX0001]  
Z8F6402AR020EC@LQFP64 [CX3011]  
Z8F6402VS020EC@PLCC68 [CX2068]  
Z8F6403FT020EC@QFP80 [CX3019]  
Z8F6421AN020AC@LQFP44 [CX3005]  
Z8F6421AN020EC@LQFP44 [CX3005]  
Z8F6421AN020SC@LQFP44 [CX3005]  
Z8F6421PM020AC [CX0001]  
Z8F6421PM020EC [CX0001]  
Z8F6421PM020SC [CX0001]  
Z8F6421VN020AC@PLCC44 [CX2044]  
Z8F6421VN020EC@PLCC44 [CX2044]  
Z8F6421VN020SC@PLCC44 [CX2044]  
Z8F6422AR020AC@LQFP64 [CX3011]  
Z8F6422AR020EC@LQFP64 [CX3011]  
Z8F6422AR020SC@LQFP64 [CX3011]  
Z8F6422VS020AC@PLCC68 [CX2068]  
Z8F6422VS020EC@PLCC68 [CX2068]  
Z8F6422VS020SC@PLCC68 [CX2068]  
Z8F6423FT020AC@QFP80 [CX3019]  
Z8F6423FT020EC@QFP80 [CX3019]  
Z8F6423FT020SC@QFP80 [CX3019]  
Z8FMC04100AKEC [CX3001]  
Z8FMC04100AKSC [CX3001]  
Z8FMC04100QKEC [CX4015]  
Z8FMC04100QKSC [CX4015]  
Z8FMC08100AKEC [CX3001]  
Z8FMC08100AKSC [CX3001]  
Z8FMC08100QKEC [CX4015]  
Z8FMC08100QKSC [CX4015]  
Z8FMC16100AKEC [CX3001]  
Z8FMC16100AKSC [CX3001]  
Z8FMC16100QKEC [CX4015]  
Z8FMC16100QKSC [CX4015]  
Z8FMC32100AKEC [CX3001]  
Z8FMC32100AKSC [CX3001]  
Z8FMC32100QKEC [CX4015]  
Z8FMC32100QKSC [CX4015]  
Z8FMC64100AKEC [CX3001]  
Z8FMC64100AKSC [CX3001]  
Z8FMC64100QKEC [CX4015]  
Z8FMC64100QKSC [CX4015]  
Z8FS011APB020EC [CX0001]  
Z8FS011APB020SC [CX0001]  
Z8FS011AQB020EC [CX4005]  
Z8FS011AQB020SC [CX4005]  
Z8FS011ASB020EC [CX1045]  
Z8FS011ASB020SC [CX1045]  
Z8FS012APB020EC [CX0001]  
Z8FS012APB020SC [CX0001]  
Z8FS012AQB020EC [CX4005]  
Z8FS012AQB020SC [CX4005]

Z8FS012AQB020SG [CX4005]	Z8FS012ASB020EC [CX1045]
Z8FS012ASB020EG [CX1045]	Z8FS012ASB020SC [CX1045]
Z8FS012ASB020SG [CX1045]	Z8FS0213HH005EC [CX1026]
Z8FS0213HH005EG [CX1026]	Z8FS0213HH005SC [CX1026]
Z8FS0213HH005SG [CX1026]	Z8FS0213HJ005EC [CX1026]
Z8FS0213HJ005EG [CX1026]	Z8FS0213HJ005SC [CX1026]
Z8FS0213HJ005SG [CX1026]	Z8FS0213PH005EC [CX0001]
Z8FS0213PH005EG [CX0001]	Z8FS0213PH005SC [CX0001]
Z8FS0213PH005SG [CX0001]	Z8FS0213PJ005EC [CX0001]
Z8FS0213PJ005EG [CX0001]	Z8FS0213PJ005SC [CX0001]
Z8FS0213PJ005SG [CX0001]	Z8FS0213SH005EC [CX1033]
Z8FS0213SH005EG [CX1033]	Z8FS0213SH005SC [CX1033]
Z8FS0213SH005SG [CX1033]	Z8FS0213SJ005EC [CX1033]
Z8FS0213SJ005EG [CX1033]	Z8FS0213SJ005SC [CX1033]
Z8FS0213SJ005SG [CX1033]	Z8FS021AHH020EC [CX1026]
Z8FS021AHH020EG [CX1026]	Z8FS021AHH020SC [CX1026]
Z8FS021AHH020SG [CX1026]	Z8FS021AHJ020EC [CX1026]
Z8FS021AHJ020EG [CX1026]	Z8FS021AHJ020SC [CX1026]
Z8FS021AHJ020SG [CX1026]	Z8FS021APB020EC [CX0001]
Z8FS021APB020EG [CX0001]	Z8FS021APB020SC [CX0001]
Z8FS021APB020SG [CX0001]	Z8FS021APH020EC [CX0001]
Z8FS021APH020EG [CX0001]	Z8FS021APH020SC [CX0001]
Z8FS021APH020SG [CX0001]	Z8FS021APJ020EC [CX0001]
Z8FS021APJ020EG [CX0001]	Z8FS021APJ020SC [CX0001]
Z8FS021APJ020SG [CX0001]	Z8FS021AQB020EC [CX4005]
Z8FS021AQB020EG [CX4005]	Z8FS021AQB020SC [CX4005]
Z8FS021AQB020SG [CX4005]	Z8FS021ASB020EC [CX1045]
Z8FS021ASB020EG [CX1045]	Z8FS021ASB020SC [CX1045]
Z8FS021ASB020SG [CX1045]	Z8FS021ASH020EC [CX1033]
Z8FS021ASH020EG [CX1033]	Z8FS021ASH020SC [CX1033]
Z8FS021ASH020SG [CX1033]	Z8FS021ASJ020EC [CX1033]
Z8FS021ASJ020EG [CX1033]	Z8FS021ASJ020SC [CX1033]
Z8FS021ASJ020SG [CX1033]	Z8FS022APB020EC [CX0001]
Z8FS022APB020EG [CX0001]	Z8FS022APB020SC [CX0001]
Z8FS022APB020SG [CX0001]	Z8FS022AQB020EC [CX4005]
Z8FS022AQB020EG [CX4005]	Z8FS022AQB020SC [CX4005]
Z8FS022AQB020SG [CX4005]	Z8FS022ASB020EC [CX1045]
Z8FS022ASB020EG [CX1045]	Z8FS022ASB020SC [CX1045]
Z8FS022ASB020SG [CX1045]	Z8FS040BPB020EC [CX0001]
Z8FS040BPB020EG [CX0001]	Z8FS040BPB020SC [CX0001]
Z8FS040BPB020SG [CX0001]	Z8FS040BQB020EC [CX4005]
Z8FS040BQB020EG [CX4005]	Z8FS040BQB020SC [CX4005]
Z8FS040BQB020SG [CX4005]	Z8FS040BSB020EC [CX1045]
Z8FS040BSB020EG [CX1045]	Z8FS040BSB020SC [CX1045]
Z8FS040BSB020SG [CX1045]	Z8FS041APB020EC [CX0001]
Z8FS041APB020EG [CX0001]	Z8FS041APB020SC [CX0001]
Z8FS041APB020SG [CX0001]	Z8FS041AQB020EC [CX4005]
Z8FS041AQB020EG [CX4005]	Z8FS041AQB020SC [CX4005]
Z8FS041AQB020SG [CX4005]	Z8FS041ASB020EC [CX1045]
Z8FS041ASB020EG [CX1045]	Z8FS041ASB020SC [CX1045]
Z8FS041ASB020SG [CX1045]	Z8FS042APB020EC [CX0001]
Z8FS042APB020EG [CX0001]	Z8FS042APB020SC [CX0001]
Z8FS042APB020SG [CX0001]	Z8FS042AQB020EC [CX4005]
Z8FS042AQB020EG [CX4005]	Z8FS042AQB020SC [CX4005]
Z8FS042AQB020SG [CX4005]	Z8FS042ASB020EC [CX1045]
Z8FS042ASB020EG [CX1045]	Z8FS042ASB020SC [CX1045]
Z8FS042ASB020SG [CX1045]	Z8FS081APB020EC [CX0001]
Z8FS081APB020EG [CX0001]	Z8FS081APB020SC [CX0001]
Z8FS081APB020SG [CX0001]	Z8FS081AQB020EC [CX4005]



Z8FS081AQB020EG [CX4005] Z8FS081AQB020SC [CX4005]  
Z8FS081AQB020SG [CX4005] Z8FS081ASB020EC [CX1045]  
Z8FS081ASB020EG [CX1045] Z8FS081ASB020SC [CX1045]  
Z8FS081ASB020SG [CX1045] Z8FS082APB020EC [CX0001]  
Z8FS082APB020EG [CX0001] Z8FS082APB020SC [CX0001]  
Z8FS082APB020SG [CX0001] Z8FS082AQB020EC [CX4005]  
Z8FS082AQB020EG [CX4005] Z8FS082AQB020SC [CX4005]  
Z8FS082AQB020SG [CX4005] Z8FS082ASB020EC [CX1045]  
Z8FS082ASB020EG [CX1045] Z8FS082ASB020SC [CX1045]  
Z8FS082ASB020SG [CX1045] Z8PE00210HEC@SSOP20 [CX1001]  
Z8PE00210HSC@SSOP20 [CX1001] Z8PE00210PEC [CX0001]  
Z8PE00210PSC [CX0001] Z8PE00210SEC@SOIC18 [CX1033]  
Z8PE00210SSC@SOIC18 [CX1033] Z8PE00210SSG@SOIC18 [CX1033]  
Z8PE00310HEC@SSOP20 [CX1001] Z8PE00310HSC@SSOP20 [CX1001]  
Z8PE00310PEC [CX0001] Z8PE00310PSC [CX0001]  
Z8PE00310SEC@SOIC18 [CX1033] Z8PE00310SSC@SOIC18 [CX1033]  
Z8PE00310SSG@SOIC18 [CX1033] ZGP323HAH2004C@SSOP20 [CX1026]  
ZGP323HAH2004G@SSOP20 [CX1026] ZGP323HAH2008C@SSOP20 [CX1026]  
ZGP323HAH2008G@SSOP20 [CX1026] ZGP323HAH2016C@SSOP20 [CX1026]  
ZGP323HAH2016G@SSOP20 [CX1026] ZGP323HAH2032C@SSOP20 [CX1026]  
ZGP323HAH2032G@SSOP20 [CX1026] ZGP323HAH2804C@SSOP28 [CX1026]  
ZGP323HAH2804G@SSOP28 [CX1026] ZGP323HAH2808C@SSOP28 [CX1026]  
ZGP323HAH2808G@SSOP28 [CX1026] ZGP323HAH2816C@SSOP28 [CX1026]  
ZGP323HAH2816G@SSOP28 [CX1026] ZGP323HAH2832C@SSOP28 [CX1026]  
ZGP323HAH2832G@SSOP28 [CX1026] ZGP323HAH4804C@SSOP48 [CX1028]  
ZGP323HAH4804G@SSOP48 [CX1028] ZGP323HAH4808C@SSOP48 [CX1028]  
ZGP323HAH4808G@SSOP48 [CX1028] ZGP323HAH4816C@SSOP48 [CX1028]  
ZGP323HAH4816G@SSOP48 [CX1028] ZGP323HAH4832C@SSOP48 [CX1028]  
ZGP323HAH4832G@SSOP48 [CX1028] ZGP323HAP2004C [CX0001]  
ZGP323HAP2004G [CX0001] ZGP323HAP2008C [CX0001]  
ZGP323HAP2008G [CX0001] ZGP323HAP2016C [CX0001]  
ZGP323HAP2016G [CX0001] ZGP323HAP2032C [CX0001]  
ZGP323HAP2032G [CX0001] ZGP323HAP2804C [CX0001]  
ZGP323HAP2804G [CX0001] ZGP323HAP2808C [CX0001]  
ZGP323HAP2808G [CX0001] ZGP323HAP2816C [CX0001]  
ZGP323HAP2816G [CX0001] ZGP323HAP2832C [CX0001]  
ZGP323HAP2832G [CX0001] ZGP323HAP4004C [CX0001]  
ZGP323HAP4004G [CX0001] ZGP323HAP4008C [CX0001]  
ZGP323HAP4008G [CX0001] ZGP323HAP4016C [CX0001]  
ZGP323HAP4016G [CX0001] ZGP323HAP4032C [CX0001]  
ZGP323HAP4032G [CX0001] ZGP323HAS2004C@SOIC20 [CX1033]  
ZGP323HAS2004G@SOIC20 [CX1033] ZGP323HAS2008C@SOIC20 [CX1033]  
ZGP323HAS2008G@SOIC20 [CX1033] ZGP323HAS2016C@SOIC20 [CX1033]  
ZGP323HAS2016G@SOIC20 [CX1033] ZGP323HAS2032C@SOIC20 [CX1033]  
ZGP323HAS2032G@SOIC20 [CX1033] ZGP323HAS2804C@SOIC28 [CX1033]  
ZGP323HAS2804G@SOIC28 [CX1033] ZGP323HAS2808C@SOIC28 [CX1033]  
ZGP323HAS2808G@SOIC28 [CX1033] ZGP323HAS2816C@SOIC28 [CX1033]  
ZGP323HAS2816G@SOIC28 [CX1033] ZGP323HAS2832C@SOIC28 [CX1033]  
ZGP323HAS2832G@SOIC28 [CX1033] ZGP323HEH2004C@SSOP20 [CX1026]  
ZGP323HEH2004G@SSOP20 [CX1026] ZGP323HEH2008C@SSOP20 [CX1026]  
ZGP323HEH2008G@SSOP20 [CX1026] ZGP323HEH2016C@SSOP20 [CX1026]  
ZGP323HEH2016G@SSOP20 [CX1026] ZGP323HEH2032C@SSOP20 [CX1026]  
ZGP323HEH2032G@SSOP20 [CX1026] ZGP323HEH2804C@SSOP28 [CX1026]  
ZGP323HEH2804G@SSOP28 [CX1026] ZGP323HEH2808C@SSOP28 [CX1026]  
ZGP323HEH2808G@SSOP28 [CX1026] ZGP323HEH2816C@SSOP28 [CX1026]  
ZGP323HEH2816G@SSOP28 [CX1026] ZGP323HEH2832C@SSOP28 [CX1026]  
ZGP323HEH2832G@SSOP28 [CX1026] ZGP323HEH4804C@SSOP48 [CX1028]  
ZGP323HEH4804G@SSOP48 [CX1028] ZGP323HEH4808C@SSOP48 [CX1028]  
ZGP323HEH4808G@SSOP48 [CX1028] ZGP323HEH4816C@SSOP48 [CX1028]

ZGP323HEH4816G@SSOP48 [CX1028]      ZGP323HEH4832C@SSOP48 [CX1028]  
ZGP323HEH4832G@SSOP48 [CX1028]      ZGP323HEP2004C [CX0001]  
ZGP323HEP2004G [CX0001]                ZGP323HEP2008C [CX0001]  
ZGP323HEP2008G [CX0001]                ZGP323HEP2016C [CX0001]  
ZGP323HEP2016G [CX0001]                ZGP323HEP2032C [CX0001]  
ZGP323HEP2032G [CX0001]                ZGP323HEP2804C [CX0001]  
ZGP323HEP2804G [CX0001]                ZGP323HEP2808C [CX0001]  
ZGP323HEP2808G [CX0001]                ZGP323HEP2816C [CX0001]  
ZGP323HEP2816G [CX0001]                ZGP323HEP2832C [CX0001]  
ZGP323HEP2832G [CX0001]                ZGP323HEP4004C [CX0001]  
ZGP323HEP4004G [CX0001]                ZGP323HEP4008C [CX0001]  
ZGP323HEP4008G [CX0001]                ZGP323HEP4016C [CX0001]  
ZGP323HEP4016G [CX0001]                ZGP323HEP4032C [CX0001]  
ZGP323HEP4032G [CX0001]                ZGP323HES2004C@SOIC20 [CX1033]  
ZGP323HES2004G@SOIC20 [CX1033]      ZGP323HES2008C@SOIC20 [CX1033]  
ZGP323HES2008G@SOIC20 [CX1033]      ZGP323HES2016C@SOIC20 [CX1033]  
ZGP323HES2016G@SOIC20 [CX1033]      ZGP323HES2032C@SOIC20 [CX1033]  
ZGP323HES2032G@SOIC20 [CX1033]      ZGP323HES2804C@SOIC28 [CX1033]  
ZGP323HES2804G@SOIC28 [CX1033]      ZGP323HES2808C@SOIC28 [CX1033]  
ZGP323HES2808G@SOIC28 [CX1033]      ZGP323HES2816C@SOIC28 [CX1033]  
ZGP323HES2816G@SOIC28 [CX1033]      ZGP323HES2832C@SOIC28 [CX1033]  
ZGP323HES2832G@SOIC28 [CX1033]      ZGP323HSH2004C@SSOP20 [CX1026]  
ZGP323HSH2004G@SSOP20 [CX1026]      ZGP323HSH2008C@SSOP20 [CX1026]  
ZGP323HSH2008G@SSOP20 [CX1026]      ZGP323HSH2016C@SSOP20 [CX1026]  
ZGP323HSH2016G@SSOP20 [CX1026]      ZGP323HSH2032C@SSOP20 [CX1026]  
ZGP323HSH2032G@SSOP20 [CX1026]      ZGP323HSH2804C@SSOP28 [CX1026]  
ZGP323HSH2804G@SSOP28 [CX1026]      ZGP323HSH2808C@SSOP28 [CX1026]  
ZGP323HSH2808G@SSOP28 [CX1026]      ZGP323HSH2816C@SSOP28 [CX1026]  
ZGP323HSH2816G@SSOP28 [CX1026]      ZGP323HSH2832C@SSOP28 [CX1026]  
ZGP323HSH2832G@SSOP28 [CX1026]      ZGP323HSH4804C@SSOP48 [CX1028]  
ZGP323HSH4804G@SSOP48 [CX1028]      ZGP323HSH4808C@SSOP48 [CX1028]  
ZGP323HSH4808G@SSOP48 [CX1028]      ZGP323HSH4816C@SSOP48 [CX1028]  
ZGP323HSH4816G@SSOP48 [CX1028]      ZGP323HSH4832C@SSOP48 [CX1028]  
ZGP323HSH4832G@SSOP48 [CX1028]      ZGP323HSP2004C [CX0001]  
ZGP323HSP2004G [CX0001]                ZGP323HSP2008C [CX0001]  
ZGP323HSP2008G [CX0001]                ZGP323HSP2016C [CX0001]  
ZGP323HSP2016G [CX0001]                ZGP323HSP2032C [CX0001]  
ZGP323HSP2032G [CX0001]                ZGP323HSP2804C [CX0001]  
ZGP323HSP2804G [CX0001]                ZGP323HSP2808C [CX0001]  
ZGP323HSP2808G [CX0001]                ZGP323HSP2816C [CX0001]  
ZGP323HSP2816G [CX0001]                ZGP323HSP2832C [CX0001]  
ZGP323HSP2832G [CX0001]                ZGP323HSP4004C [CX0001]  
ZGP323HSP4004G [CX0001]                ZGP323HSP4008C [CX0001]  
ZGP323HSP4008G [CX0001]                ZGP323HSP4016C [CX0001]  
ZGP323HSP4016G [CX0001]                ZGP323HSP4032C [CX0001]  
ZGP323HSP4032G [CX0001]                ZGP323HSS2004C@SOIC20 [CX1033]  
ZGP323HSS2004G@SOIC20 [CX1033]      ZGP323HSS2008C@SOIC20 [CX1033]  
ZGP323HSS2008G@SOIC20 [CX1033]      ZGP323HSS2016C@SOIC20 [CX1033]  
ZGP323HSS2016G@SOIC20 [CX1033]      ZGP323HSS2032C@SOIC20 [CX1033]  
ZGP323HSS2032G@SOIC20 [CX1033]      ZGP323HSS2804C@SOIC28 [CX1033]  
ZGP323HSS2804G@SOIC28 [CX1033]      ZGP323HSS2808C@SOIC28 [CX1033]  
ZGP323HSS2808G@SOIC28 [CX1033]      ZGP323HSS2816C@SOIC28 [CX1033]  
ZGP323HSS2816G@SOIC28 [CX1033]      ZGP323HSS2832C@SOIC28 [CX1033]  
ZGP323HSS2832G@SOIC28 [CX1033]      ZGP323LAH2004C@SSOP20 [CX1026]  
ZGP323LAH2004G@SSOP20 [CX1026]      ZGP323LAH2008C@SSOP20 [CX1026]  
ZGP323LAH2008G@SSOP20 [CX1026]      ZGP323LAH2016C@SSOP20 [CX1026]  
ZGP323LAH2016G@SSOP20 [CX1026]      ZGP323LAH2032C@SSOP20 [CX1026]  
ZGP323LAH2032G@SSOP20 [CX1026]      ZGP323LAH2804C@SSOP28 [CX1026]  
ZGP323LAH2804G@SSOP28 [CX1026]      ZGP323LAH2808C@SSOP28 [CX1026]

ZGP323LAH2808G@SSOP28 [CX1026]      ZGP323LAH2816C@SSOP28 [CX1026]  
ZGP323LAH2816G@SSOP28 [CX1026]      ZGP323LAH2832C@SSOP28 [CX1026]  
ZGP323LAH2832G@SSOP28 [CX1026]      ZGP323LAH4804C@SSOP48 [CX1028]  
ZGP323LAH4804G@SSOP48 [CX1028]      ZGP323LAH4808C@SSOP48 [CX1028]  
ZGP323LAH4808G@SSOP48 [CX1028]      ZGP323LAH4816C@SSOP48 [CX1028]  
ZGP323LAH4816G@SSOP48 [CX1028]      ZGP323LAH4832C@SSOP48 [CX1028]  
ZGP323LAH4832G@SSOP48 [CX1028]      ZGP323LAP2004C [CX0001]  
ZGP323LAP2004G [CX0001]      ZGP323LAP2008C [CX0001]  
ZGP323LAP2008G [CX0001]      ZGP323LAP2016C [CX0001]  
ZGP323LAP2016G [CX0001]      ZGP323LAP2032C [CX0001]  
ZGP323LAP2032G [CX0001]      ZGP323LAP2804C [CX0001]  
ZGP323LAP2804G [CX0001]      ZGP323LAP2808C [CX0001]  
ZGP323LAP2808G [CX0001]      ZGP323LAP2816C [CX0001]  
ZGP323LAP2816G [CX0001]      ZGP323LAP2832C [CX0001]  
ZGP323LAP2832G [CX0001]      ZGP323LAP4004C [CX0001]  
ZGP323LAP4004G [CX0001]      ZGP323LAP4008C [CX0001]  
ZGP323LAP4008G [CX0001]      ZGP323LAP4016C [CX0001]  
ZGP323LAP4016G [CX0001]      ZGP323LAP4032C [CX0001]  
ZGP323LAP4032G [CX0001]      ZGP323LAS2004C@SOIC20 [CX1033]  
ZGP323LAS2004G@SOIC20 [CX1033]      ZGP323LAS2008C@SOIC20 [CX1033]  
ZGP323LAS2008G@SOIC20 [CX1033]      ZGP323LAS2016C@SOIC20 [CX1033]  
ZGP323LAS2016G@SOIC20 [CX1033]      ZGP323LAS2032C@SOIC20 [CX1033]  
ZGP323LAS2032G@SOIC20 [CX1033]      ZGP323LAS2804C@SOIC28 [CX1033]  
ZGP323LAS2804G@SOIC28 [CX1033]      ZGP323LAS2808C@SOIC28 [CX1033]  
ZGP323LAS2808G@SOIC28 [CX1033]      ZGP323LAS2816C@SOIC28 [CX1033]  
ZGP323LAS2816G@SOIC28 [CX1033]      ZGP323LAS2832C@SOIC28 [CX1033]  
ZGP323LAS2832G@SOIC28 [CX1033]      ZGP323LEH2004C@SSOP20 [CX1026]  
ZGP323LEH2004G@SSOP20 [CX1026]      ZGP323LEH2008C@SSOP20 [CX1026]  
ZGP323LEH2008G@SSOP20 [CX1026]      ZGP323LEH2016C@SSOP20 [CX1026]  
ZGP323LEH2016G@SSOP20 [CX1026]      ZGP323LEH2032C@SSOP20 [CX1026]  
ZGP323LEH2032G@SSOP20 [CX1026]      ZGP323LEH2804C@SSOP28 [CX1026]  
ZGP323LEH2804G@SSOP28 [CX1026]      ZGP323LEH2808C@SSOP28 [CX1026]  
ZGP323LEH2808G@SSOP28 [CX1026]      ZGP323LEH2816C@SSOP28 [CX1026]  
ZGP323LEH2816G@SSOP28 [CX1026]      ZGP323LEH2832C@SSOP28 [CX1026]  
ZGP323LEH2832G@SSOP28 [CX1026]      ZGP323LEH4804C@SSOP48 [CX1028]  
ZGP323LEH4804G@SSOP48 [CX1028]      ZGP323LEH4808C@SSOP48 [CX1028]  
ZGP323LEH4808G@SSOP48 [CX1028]      ZGP323LEH4816C@SSOP48 [CX1028]  
ZGP323LEH4816G@SSOP48 [CX1028]      ZGP323LEH4832C@SSOP48 [CX1028]  
ZGP323LEH4832G@SSOP48 [CX1028]      ZGP323LEP2004C [CX0001]  
ZGP323LEP2004G [CX0001]      ZGP323LEP2008C [CX0001]  
ZGP323LEP2008G [CX0001]      ZGP323LEP2016C [CX0001]  
ZGP323LEP2016G [CX0001]      ZGP323LEP2032C [CX0001]  
ZGP323LEP2032G [CX0001]      ZGP323LEP2804C [CX0001]  
ZGP323LEP2804G [CX0001]      ZGP323LEP2808C [CX0001]  
ZGP323LEP2808G [CX0001]      ZGP323LEP2816C [CX0001]  
ZGP323LEP2816G [CX0001]      ZGP323LEP2832C [CX0001]  
ZGP323LEP2832G [CX0001]      ZGP323LEP4004C [CX0001]  
ZGP323LEP4004G [CX0001]      ZGP323LEP4008C [CX0001]  
ZGP323LEP4008G [CX0001]      ZGP323LEP4016C [CX0001]  
ZGP323LEP4016G [CX0001]      ZGP323LEP4032C [CX0001]  
ZGP323LEP4032G [CX0001]      ZGP323LES2004C@SOIC20 [CX1033]  
ZGP323LES2004G@SOIC20 [CX1033]      ZGP323LES2008C@SOIC20 [CX1033]  
ZGP323LES2008G@SOIC20 [CX1033]      ZGP323LES2016C@SOIC20 [CX1033]  
ZGP323LES2016G@SOIC20 [CX1033]      ZGP323LES2032C@SOIC20 [CX1033]  
ZGP323LES2032G@SOIC20 [CX1033]      ZGP323LES2804C@SOIC28 [CX1033]  
ZGP323LES2804G@SOIC28 [CX1033]      ZGP323LES2808C@SOIC28 [CX1033]  
ZGP323LES2808G@SOIC28 [CX1033]      ZGP323LES2816C@SOIC28 [CX1033]  
ZGP323LES2816G@SOIC28 [CX1033]      ZGP323LES2832C@SOIC28 [CX1033]  
ZGP323LES2832G@SOIC28 [CX1033]      ZGP323LSH2004C@SSOP20 [CX1026]

ZGP323LSH2004G@SSOP20 [CX1026]      ZGP323LSH2008C@SSOP20 [CX1026]  
ZGP323LSH2008G@SSOP20 [CX1026]      ZGP323LSH2016C@SSOP20 [CX1026]  
ZGP323LSH2016G@SSOP20 [CX1026]      ZGP323LSH2032C@SSOP20 [CX1026]  
ZGP323LSH2032G@SSOP20 [CX1026]      ZGP323LSH2804C@SSOP28 [CX1026]  
ZGP323LSH2804G@SSOP28 [CX1026]      ZGP323LSH2808C@SSOP28 [CX1026]  
ZGP323LSH2808G@SSOP28 [CX1026]      ZGP323LSH2816C@SSOP28 [CX1026]  
ZGP323LSH2816G@SSOP28 [CX1026]      ZGP323LSH2832C@SSOP28 [CX1026]  
ZGP323LSH2832G@SSOP28 [CX1026]      ZGP323LSH4804C@SSOP48 [CX1028]  
ZGP323LSH4804G@SSOP48 [CX1028]      ZGP323LSH4808C@SSOP48 [CX1028]  
ZGP323LSH4808G@SSOP48 [CX1028]      ZGP323LSH4816C@SSOP48 [CX1028]  
ZGP323LSH4816G@SSOP48 [CX1028]      ZGP323LSH4832C@SSOP48 [CX1028]  
ZGP323LSH4832G@SSOP48 [CX1028]      ZGP323LSK2032E [CX0001]  
ZGP323LSK2032G [CX0001]      ZGP323LSK2832E [CX0001]  
ZGP323LSK2832G [CX0001]      ZGP323LSK4032E [CX0001]  
ZGP323LSK4032G [CX0001]      ZGP323LSP2004C [CX0001]  
ZGP323LSP2004G [CX0001]      ZGP323LSP2008C [CX0001]  
ZGP323LSP2008G [CX0001]      ZGP323LSP2016C [CX0001]  
ZGP323LSP2016G [CX0001]      ZGP323LSP2032C [CX0001]  
ZGP323LSP2032G [CX0001]      ZGP323LSP2804C [CX0001]  
ZGP323LSP2804G [CX0001]      ZGP323LSP2808C [CX0001]  
ZGP323LSP2808G [CX0001]      ZGP323LSP2816C [CX0001]  
ZGP323LSP2816G [CX0001]      ZGP323LSP2832C [CX0001]  
ZGP323LSP2832G [CX0001]      ZGP323LSP4004C [CX0001]  
ZGP323LSP4004G [CX0001]      ZGP323LSP4008C [CX0001]  
ZGP323LSP4008G [CX0001]      ZGP323LSP4016C [CX0001]  
ZGP323LSP4016G [CX0001]      ZGP323LSP4032C [CX0001]  
ZGP323LSP4032G [CX0001]      ZGP323LSS2004C@SOIC20 [CX1033]  
ZGP323LSS2004G@SOIC20 [CX1033]      ZGP323LSS2008C@SOIC20 [CX1033]  
ZGP323LSS2008G@SOIC20 [CX1033]      ZGP323LSS2016C@SOIC20 [CX1033]  
ZGP323LSS2016G@SOIC20 [CX1033]      ZGP323LSS2032C@SOIC20 [CX1033]  
ZGP323LSS2032G@SOIC20 [CX1033]      ZGP323LSS2804C@SOIC28 [CX1033]  
ZGP323LSS2804G@SOIC28 [CX1033]      ZGP323LSS2808C@SOIC28 [CX1033]  
ZGP323LSS2808G@SOIC28 [CX1033]      ZGP323LSS2816C@SOIC28 [CX1033]  
ZGP323LSS2816G@SOIC28 [CX1033]      ZGP323LSS2832C@SOIC28 [CX1033]  
ZGP323LSS2832G@SOIC28 [CX1033]      ZLF645E0H2032G@SSOP20 [CX1026]  
ZLF645E0H2064G@SSOP20 [CX1026]      ZLF645E0H2832G@SSOP28 [CX1026]  
ZLF645E0H2864G@SSOP28 [CX1026]      ZLF645E0P2032G [CX0001]  
ZLF645E0P2064G [CX0001]      ZLF645E0P2832G [CX0001]  
ZLF645E0P2864G [CX0001]      ZLF645E0Q2032G@QFN20 [CX4013]  
ZLF645E0Q2064G@QFN20 [CX4013]      ZLF645E0S2032G@SOIC20 [CX1033]  
ZLF645E0S2064G@SOIC20 [CX1033]      ZLF645E0S2832G@SOIC28 [CX1033]  
ZLF645E0S2864G@SOIC28 [CX1033]      ZLF645S0H2032G@SSOP20 [CX1026]  
ZLF645S0H2064G@SSOP20 [CX1026]      ZLF645S0H2832G@SSOP28 [CX1026]  
ZLF645S0H2864G@SSOP28 [CX1026]      ZLF645S0P2032G [CX0001]  
ZLF645S0P2064G [CX0001]      ZLF645S0P2832G [CX0001]  
ZLF645S0P2864G [CX0001]      ZLF645S0Q2032G@QFN20 [CX4013]  
ZLF645S0Q2064G@QFN20 [CX4013]      ZLF645S0S2032G@SOIC20 [CX1033]  
ZLF645S0S2064G@SOIC20 [CX1033]      ZLF645S0S2832G@SOIC28 [CX1033]  
ZLF645S0S2864G@SOIC28 [CX1033]      ZLP12840H2028C@SSOP20 [CX1026]  
ZLP12840H2028G@SSOP20 [CX1026]      ZLP12840H2032C@SSOP20 [CX1026]  
ZLP12840H2032G@SSOP20 [CX1026]      ZLP12840H2064C@SSOP20 [CX1026]  
ZLP12840H2064G@SSOP20 [CX1026]      ZLP12840H2096C@SSOP20 [CX1026]  
ZLP12840H2096G@SSOP20 [CX1026]      ZLP12840H2828C@SSOP28 [CX1026]  
ZLP12840H2828G@SSOP28 [CX1026]      ZLP12840H2832C@SSOP28 [CX1026]  
ZLP12840H2832G@SSOP28 [CX1026]      ZLP12840H2864C@SSOP28 [CX1026]  
ZLP12840H2864G@SSOP28 [CX1026]      ZLP12840H2896C@SSOP28 [CX1026]  
ZLP12840H2896G@SSOP28 [CX1026]      ZLP12840P2028C [CX0001]  
ZLP12840P2028G [CX0001]      ZLP12840P2032C [CX0001]  
ZLP12840P2032G [CX0001]      ZLP12840P2064C [CX0001]

ZLP12840P2064G [CX0001]  
ZLP12840P2096G [CX0001]  
ZLP12840P2828G [CX0001]  
ZLP12840P2832G [CX0001]  
ZLP12840P2864G [CX0001]  
ZLP12840P2896G [CX0001]  
ZLP12840S2028G@SOIC20 [CX1033]  
ZLP12840S2032G@SOIC20 [CX1033]  
ZLP12840S2064G@SOIC20 [CX1033]  
ZLP12840S2096G@SOIC20 [CX1033]  
ZLP12840S2828G@SOIC28 [CX1033]  
ZLP12840S2832G@SOIC28 [CX1033]  
ZLP12840S2864G@SOIC28 [CX1033]  
ZLP12840S2896G@SOIC28 [CX1033]  
ZLP32300H2004G@SSOP20 [CX1026]  
ZLP32300H2008G@SSOP20 [CX1026]  
ZLP32300H2016G@SSOP20 [CX1026]  
ZLP32300H2032G@SSOP20 [CX1026]  
ZLP32300H2804G@SSOP28 [CX1026]  
ZLP32300H2808G@SSOP28 [CX1026]  
ZLP32300H2816G@SSOP28 [CX1026]  
ZLP32300H2832G@SSOP28 [CX1026]  
ZLP32300H4804G@SSOP48 [CX1028]  
ZLP32300H4808G@SSOP48 [CX1028]  
ZLP32300H4816G@SSOP48 [CX1028]  
ZLP32300H4832G@SSOP48 [CX1028]  
ZLP32300P2004G [CX0001]  
ZLP32300P2008G [CX0001]  
ZLP32300P2016G [CX0001]  
ZLP32300P2032G [CX0001]  
ZLP32300P2804G [CX0001]  
ZLP32300P2808G [CX0001]  
ZLP32300P2816G [CX0001]  
ZLP32300P2832G [CX0001]  
ZLP32300P4004G [CX0001]  
ZLP32300P4008G [CX0001]  
ZLP32300P4016G [CX0001]  
ZLP32300P4032G [CX0001]  
ZLP32300S2004G@SOIC20 [CX1033]  
ZLP32300S2008G@SOIC20 [CX1033]  
ZLP32300S2016G@SOIC20 [CX1033]  
ZLP32300S2032G@SOIC20 [CX1033]  
ZLP32300S2804G@SOIC28 [CX1033]  
ZLP32300S2808G@SOIC28 [CX1033]  
ZLP32300S2816G@SOIC28 [CX1033]  
ZLP32300S2832G@SOIC28 [CX1033]  
ZLP12840P2096C [CX0001]  
ZLP12840P2828C [CX0001]  
ZLP12840P2832C [CX0001]  
ZLP12840P2864C [CX0001]  
ZLP12840P2896C [CX0001]  
ZLP12840S2028C@SOIC20 [CX1033]  
ZLP12840S2032C@SOIC20 [CX1033]  
ZLP12840S2064C@SOIC20 [CX1033]  
ZLP12840S2096C@SOIC20 [CX1033]  
ZLP12840S2828C@SOIC28 [CX1033]  
ZLP12840S2832C@SOIC28 [CX1033]  
ZLP12840S2864C@SOIC28 [CX1033]  
ZLP12840S2896C@SOIC28 [CX1033]  
ZLP32300H2004C@SSOP20 [CX1026]  
ZLP32300H2008C@SSOP20 [CX1026]  
ZLP32300H2016C@SSOP20 [CX1026]  
ZLP32300H2032C@SSOP20 [CX1026]  
ZLP32300H2804C@SSOP28 [CX1026]  
ZLP32300H2808C@SSOP28 [CX1026]  
ZLP32300H2816C@SSOP28 [CX1026]  
ZLP32300H2832C@SSOP28 [CX1026]  
ZLP32300H4804C@SSOP48 [CX1028]  
ZLP32300H4808C@SSOP48 [CX1028]  
ZLP32300H4816C@SSOP48 [CX1028]  
ZLP32300H4832C@SSOP48 [CX1028]  
ZLP32300P2004C [CX0001]  
ZLP32300P2008C [CX0001]  
ZLP32300P2016C [CX0001]  
ZLP32300P2032C [CX0001]  
ZLP32300P2804C [CX0001]  
ZLP32300P2808C [CX0001]  
ZLP32300P2816C [CX0001]  
ZLP32300P2832C [CX0001]  
ZLP32300P4004C [CX0001]  
ZLP32300P4008C [CX0001]  
ZLP32300P4016C [CX0001]  
ZLP32300P4032C [CX0001]  
ZLP32300S2004C@SOIC20 [CX1033]  
ZLP32300S2008C@SOIC20 [CX1033]  
ZLP32300S2016C@SOIC20 [CX1033]  
ZLP32300S2032C@SOIC20 [CX1033]  
ZLP32300S2804C@SOIC28 [CX1033]  
ZLP32300S2808C@SOIC28 [CX1033]  
ZLP32300S2816C@SOIC28 [CX1033]  
ZLP32300S2832C@SOIC28 [CX1033]

## ZMD

### E (E) PROM/FRAM/NVRAM

U62256 [CX0001]  
U6264@SOIC28  
U6264A@SOIC28 [CX1035]  
U62H256S@SOIC28 [CX1035]  
U630H16 [CX0001]  
U630H64 [CX0001]  
U631H16 [CX0001]  
U6264 [CX0001]  
U6264A [CX0001]  
U62H256A@SOIC28 [CX1035]  
U62H64SA@SOIC28 [CX1033]  
U630H16@SOIC28 [CX1035]  
U630H64@SOIC28 [CX1035]  
U631H16@SOIC24 [CX1033]

U631H16@SOIC28 [CX1035]	U631H256 [CX0001]
U631H256@SOIC28 [CX1035]	U631H64 [CX0001]
U631H64@SOIC28 [CX1035]	U632H16 [CX0001]
U632H16@SOIC28 [CX1035]	U632H64 [CX0001]
U632H64@SOIC28 [CX1035]	U634H256 [CX0001]
U634H256@SOIC32 [CX1035]	U635H16 [CX0001]
U635H16@SOIC24 [CX1033]	U635H256 [CX0001]
U635H256@SOIC28 [CX1035]	U635H64 [CX0001]
U635H64@SOIC28 [CX1035]	U63716 [CX0001]
U637256 [CX0001]	U63764 [CX0001]
U637H256 [CX0001]	UL62H256A@SOIC28 [CX1035]
UL631H256@SOIC28 [CX1035]	UL631H256@TSOP32 [CX1002]
UL634H256@SOIC32 [CX1035]	UL634H256@TSOP32 [CX1002]
UL635H256@SOIC28 [CX1035]	UL635H256@SOIC32 [CX1002]