

# PRODUCT Information

P.B. 177 • N-1601 Fredrikstad • Norway  
+47 69 36 43 00 • Fax: +47 69 32 94 33  
salg@mascot.no • www.mascot.no

## MODEL 9780

### AC/AC PLUG-IN ADAPTER

- **Max 18 VA output power**
- **230 VAC input voltage**
- **Available with EU and UK terminals**
- **Compliance with relevant worldwide safety standards**
- **Exchangeable output plugs, providing:**
  - reduced stocking requirements
  - short delivery lead times
  - snap-locks for added safety



#### Technical Specifications

		12 V	12 V
<b>Input voltage:</b>	VAC	230 VAC, 50 Hz	
<b>Output voltage:</b>	VAC	12	12
<b>Max. output power:</b>	VA	12	18
<b>Max. Load current:</b>	A	1	1,5
<b>Temperature range:</b>	°C	-10°C to +40	
<b>Protection:</b>		Thermal fuse in primary	
<b>Insulation class:</b>		II	
<b>Electrical safety</b>		EN 60950	
<b>EMC, Emission</b>		EN50081-1	
<b>EMC, Immunity</b>		EN50082-1	
<b>Mains connections:</b>		EU and UK	
<b>Output terminals:</b>		Secondary cable w/snap-on plugs	
<b>Dimensions (EU mod):</b>	mm	63x51x42	74x58x47
<b>Dimensions (UK mod):</b>	mm	83x57x55	
<b>Weight:</b>	g	EU: 320, UK: 440	EU: 460, UK: 470

#### EXCHANGEABLE OUTPUT PLUGS

With snap-locks



For added safety  
both plug ends are clearly  
marked to connect desired polarity.

With reservations against misprint and changes in product specifications

pi9780J-e / 190301 / s.1/1

**Mascot UK**  
P.O. Box 1560, Andover  
SP11 8QZ HAMPSHIRE  
UK  
Phone: +44 (0)1264 357177  
Fax: +44 (0)1264 364055

**Mascot Deutschland**  
Mooshaldenweg 5  
D-88069 TETTANANG  
Germany  
Phone: +49 7542 953540  
Fax: +49 7542 953560

**Mascot AS - Succursale France**  
23 Clos du Perthuis  
F-14200 HEROUVILLE ST. CLAIR  
France  
Phone: +33 (0)231 06 04 40  
Fax: +33 (0)231 06 04 50

**Mascot Benelux**  
Wilderstraat 52  
B-9400 APPELTERRE  
Belgium  
Phone: +32 (0) 54 600 442  
Phone: +32 (0) 54 600 443

**Mascot AS - Swedish Office**  
Phone: +46 (0) 526 14025  
Fax: +46 (0) 526 15513