

M18 FID3-O

M18 FUEL™ 1/4" HEX IMPACT DRIVER

- Higher power efficiency under load with outstanding torque of 226 Nm
- Faster driving speed vs. previous model, up to 3900 rpm and 4400 ipm
- Extremely compact design, total length of just 113 mm for access into tight spaces
- DRIVE CONTROL allows the user to shift into four different speed and torque settings to maximise application versatility
- Mode 1 for precision work
- Mode 2 helps prevent damage to fasteners and material
- Mode 3 delivers maximum performance for the toughest applications
- Mode 4 is the optimum between precision work and maximum performance and automatically adjusts speed, impacts and torque
- Individual battery cell monitoring optimises tool run time and ensures long term pack durability
- 1/4" Hex chuck for quick and easy bit change
- The DNA of our FUEL™ platform redefines the balance of cordless technologies. MILWAUKEE®'s POWERSTATE™ brushless motor, REDLITHIUM™ battery pack and REDLINK PLUS™ electronic intelligence delivering outstanding power, run time and durability
- Flexible battery system: works with all MILWAUKEE® M18™ batteries



REDLITHIUM™

No load speed (rpm)	1750/3000/3900/0-3900
Impact rate (ipm)	1400/3600/4400/0-4400
Max. torque (Nm)	226
Tool reception	1/4" Hex
Weight with battery pack (EPTA) (kg)	1.7 (M18 B5)
Kit included	No batteries supplied, No charger supplied, No kitbox or bag supplied
Article number	4933498061