

FR50 - Flame Resistant Anti-Static

Coverall 350g

Collection: Bizflame™ Work

Range: Flame Resistant

Shell Fabric: Bizflame Work: 99% Cotton, 1% Carbon Fibre

Outer Carton: 12



Product information

This coverall is perfect for the demands of the offshore industry. Constructed with a highly innovative flame-retardant fabric with high visibility reflective tape double stitched for enhanced visibility. Meeting all the required EN standards, features include triple stitched seams, high visibility strips on shoulders, arms and legs, concealed 2-way front brass zip and two front slant chest pockets with concealed brass zips.

Bizflame™ Work

BizFlame™ Work has been developed and designed using the highly innovative Bizflame™ Work flame resistant fabric with added anti-static properties. Certified to a range of international standards. Triple stitching and brass zips throughout for extra strength and durability.

Flame Resistant

This industry leading flame resistant range provides multi standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1+A2, B1, C1, E2, F1)

EN ISO 11611 Class 2 (A1+A2)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 8.6 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

ASTM F1959/F1959M-12 (ATPV=13.6 Cal/CM² (HAF=82%))

Features

- Protection against radiant, convective and contact heat
- Class 2 welding protection
- Rule pocket
- Two back patch pockets
- Hook and loop cuffs for a secure fit
- Action back for extra freedom of movement
- Concealed zip pocket
- Available in sizes from XS to 6XL
- Triple-stitched seams for extra durability
- 10 pockets for ample storage
- 40+ UPF rated fabric to block 98% of UV rays

FR50 - Flame Resistant Anti-Static Coverall 350g
Commodity Code: 6211321000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/13136-02/E00-00

OETI (Institut fuer Oekologie, Technik und Innovation GmbH) (Notified Body No.: 0534)
 Sebenhirtenstrasse 12A
 1230, Austria
 Contact: Marion Pfeiler
 Cert No: 0598

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	DUN14
FR50RERXS	Red	43.0	28.0	50.0	1.5200	0.0602	5036108244249	15036108732750
FR50RERS	Red	43.0	28.0	50.0	1.5800	0.0602	5036108167371	15036108625984
FR50RERM	Red	43.0	28.0	50.0	1.6000	0.0602	5036108167364	15036108625977
FR50RERL	Red	43.0	28.0	50.0	1.6300	0.0602	5036108167357	15036108625960
FR50RERXL	Red	43.0	28.0	50.0	1.6900	0.0602	5036108167388	15036108625991
FR50RERXXL	Red	43.0	28.0	55.0	1.7600	0.0662	5036108167395	15036108626004
FR50RERXXXL	Red	43.0	28.0	55.0	1.8900	0.0662	5036108167401	15036108626011
FR50RER4XL	Red	43.0	28.0	55.0	1.9600	0.0662	5036108244263	15036108732774
FR50RER5XL	Red	43.0	28.0	55.0	2.0100	0.0662	5036108298969	15036108788535