



Pushing Performance  
Since 1945

# 25p STR MA PL2\_M3 nut\_Reel\_140 pcs



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                     |
|--------------------|-------------------------------------------------------------------------------------|
| Part number        | 09 55 329 6811 741                                                                  |
| Specification      | 25p STR MA PL2_M3 nut_Reel_140 pcs                                                  |
| HARTING eCatalogue | <a href="https://harting.com/09553296811741">https://harting.com/09553296811741</a> |

## Identification

|                            |                     |
|----------------------------|---------------------|
| Category                   | Connectors          |
| Series                     | D-Sub               |
| Identification             | Standard            |
| Element                    | Connector           |
| Description of the contact | Stamped<br>Straight |

## Version

|                    |                                          |
|--------------------|------------------------------------------|
| Termination method | Reflow soldering termination (SMT)       |
| Gender             | Male                                     |
| Size               | D-Sub 3                                  |
| Connection type    | Motherboard to daughtercard<br>Mezzanine |
| Number of contacts | 25                                       |
| Locking type       | Fixing flange with thread M3             |
| Pack contents      | 140 pieces on reel                       |

## Technical characteristics

|                                    |                         |
|------------------------------------|-------------------------|
| Contact spacing (termination side) | 2.76 mm                 |
| Rated current                      | 5 A                     |
| Clearance distance                 | ≥1 mm                   |
| Creepage distance                  | ≥1 mm                   |
| Insulation resistance              | > 5 x 10 <sup>9</sup> Ω |
| Contact resistance                 | ≤25 mΩ                  |



**Pushing Performance**  
Since 1945

## Technical characteristics

|                                  |                                                                 |
|----------------------------------|-----------------------------------------------------------------|
| Tightening torque                | ≤0.6 Nm Female screw lock                                       |
| Limiting temperature             | -55 ... +125 °C (during reflow soldering max. +240 °C for 30 s) |
| Insertion force                  | ≤83 N                                                           |
| Withdrawal force                 | ≥7.8 N<br>≤56 N                                                 |
| Performance level                | 2<br>acc. to CECC 75301-802                                     |
| Mating cycles                    | ≥250                                                            |
| Test voltage $U_{r.m.s.}$        | 1 kV                                                            |
| Isolation group                  | IIIa ( $175 \leq CTI < 400$ )                                   |
| PCB thickness                    | ≥1.6 mm                                                         |
| Installation height              | 6.35 mm                                                         |
| Hot plugging                     | No                                                              |
| Moisture Sensitivity Level (MSL) | 1 acc. to ECA/IPC/JEDEC J-STD-020D                              |
| Process Sensitivity Level (PSL)  | R0 acc. to ECA/IPC/JEDEC J-STD-020D                             |

## Material properties

|                                           |                                                             |
|-------------------------------------------|-------------------------------------------------------------|
| Material (insert)                         | Liquid crystal polymer (LCP)<br>Shell: steel, nickel plated |
| Colour (insert)                           | Black                                                       |
| Material (contacts)                       | Copper alloy                                                |
| Surface (contacts)                        | Noble metal over Ni                                         |
| Material flammability class acc. to UL 94 | V-0                                                         |
| RoHS                                      | compliant                                                   |
| ELV status                                | compliant                                                   |
| China RoHS                                | e                                                           |
| REACH Annex XVII substances               | Not contained                                               |
| REACH ANNEX XIV substances                | Not contained                                               |
| REACH SVHC substances                     | Not contained                                               |
| California Proposition 65 substances      | Not contained                                               |

## Specifications and approvals

|                |           |
|----------------|-----------|
| Specifications | DIN 41652 |
|----------------|-----------|



Pushing Performance  
Since 1945

Specifications and approvals

|          |                                   |
|----------|-----------------------------------|
| UL / CSA | UL 1977 ECBT2.E102079             |
|          | CSA-C22.2 No. 182.3 ECBT8.E102079 |

Commercial data

|                                |                        |
|--------------------------------|------------------------|
| Packaging size                 | 1                      |
| Net weight                     | 1,950 g                |
| Country of origin              | Vietnam                |
| European customs tariff number | 85366990               |
| GTIN                           | 5713140069893          |
| ETIM                           | EC001136               |
| eCl@ss                         | 27440214 D-Sub coupler |