

Model No. 406TEAL

Teal Dielectric Zenex™ Thermoplastic Safety Padlock, 1-1/2in (38mm) Wide with 1-1/2in (38mm) Tall Nylon Shackle

Best Used For:

LOCKOUT/ TAGOUT Lockout Tagout

LOCKOUT/ TAGOUT Safety Lockout/Tagout

Overview & Features

Product Features

- 406 Dielectric Thermoplastic Safety Padlock
- Plastic shackle helps prevent electrocution and arc flashing, also prevents electrical current from shackle to key
- All components are non-sparking and non-magnetic - plastic, copper, brass
- 1-1/2in (38mm) wide, 1-3/4in (45mm) tall, Thermoplastic teal body, plastic shackle with 1-1/2in (38mm) clearance
- Designed exclusively for lockout tagout applications
- Durable, lightweight, non-conductive Thermoplastic lock body
- Compliance with "One Employee, One Lock, One Key" directive
- Key retaining - ensures that padlock is not left unlocked
- Keyed different, 6-pin tumbler with over 40,000 available key changes cylinder
- Commercial Packaging, Shelf Pack Qty 6, Master Carton Qty 36

Certifications


-

Product Details

The Master Lock No. 406TEAL Dielectric Thermoplastic Safety Padlock features a 1-1/2in (38mm) wide Zenex™ Thermoplastic teal body and a 1-1/2in (38mm) tall, 1/4in (6mm) diameter plastic shackle to help prevent electrocution and arc flashing and to prevent electrical current from shackle to key. All components are non-sparking and non-magnetic. Designed exclusively for Lockout/Tagout applications, the durable, lightweight material is easy to carry and padlock has key retaining cylinder to ensure the padlock is not left unlocked.

Product Specifications

Product Number	406TEAL
Body Width	38mm
Shackle Dimensions	A: 6 mm B: 38 mm C: 20 mm
Colour	Teal
Description	Keyed Different, Commercial Boxed Packaging
Shelf Pack Qty	6
Master Carton Qty	36



Master Lock Europe S.A.S.
10 avenue de l'arche - Le Colisée Gardens, bâtiment A - 92 400 Courbevoie - La Défense - France
O:+33-1-41437200 | F:+33-1-41437204
www.masterlock.eu