



PRODUCT-DETAILS

CP4-13Y-10

CP4-13Y-10 Pushbutton



概要信息	
产品型号	CP4-13Y-10
产品ID	1SFA619103R1313
欧洲商品编号(EAN)	7320500553701
目录说明	CP4-13Y-10 Pushbutton
详细描述	The CP4-13Y-10 Pushbutton is: Compact - Pushbutton - Maintained - Extended - Yellow - Illuminated - Black Plastic - 1NO - Yellow - 1 NO - 0 NC - 230 V This Pushbutton is part of ABB's compact range, the most efficient all-in-one solution available, reducing installation time and cost. The compact range has a high level of dust and water resistance.

订货信息	
最小起订量	10 piece
海关关税号	8536508090

Popular Downloads	
数据手册, 技术资料	1SFC151007C02_

尺寸

产品净宽	0.03 m
产品净高	0.03 m
产品净深	0.055 m
产品净重	0.025 kg

技术参数

周围环境温度	Operation -25 ... +70 °C Storage -40 ... +85 °C
颜色	Yellow
驱动器类型	Extended
座圈材料	Black Plastic
照明	Illuminated
灯类型	LED 220V AC/DC
功能	Maintained
辅助触点NC数量	0
辅助触点NO数量	1
外壳防护等级	1 级 12 级 13 级 3R 级 4 级 4X 级
污染等级	3
额定绝缘电压 (U _i)	300 V
额定冲击耐受电压 (U _{imp})	6 kV
额定频率 (f)	50 / 60 Hz Supply Circuit 50 / 60 Hz
额定工作电压	230 V AC/DC Maximum 300 V Supply Circuit 230 V AC/DC
额定工作电流 DC-13 (I _e)	(24 V) 0.3 A (125 V) 0.2 A
额定工作电流 AC-15 (I _e)	(120 V) 1.5 A (240 V) 1 A
功率损耗	Maximum 2.5 W
机械寿命	0.5 million
连接容量	Flexible with Ferrule 1 x 0.5...1.5 mm ² Flexible with Ferrule 2 x 0.5...1.5 mm ² Flexible with Insulated Ferrule 1 x 0.5...1.5 mm ² Flexible with Insulated Ferrule 2 x 0.5...1.5 mm ² Flexible 1 x 0.5 ...1.5 mm ² Flexible 2 x 0.5 ...1.5 mm ² Solid 1 x 0.5...1.5 mm ² Solid 2 x 0.5...1.5 mm ²
连接类型	Screw Clamp
端子类型	Screw Terminals
拧紧力矩	0.8 N·m
剥线长度	6 mm

UL/CSA适用的技术参数

连接容量UL/CSA	1x 22...14 AWG
	2x 22...14 AWG

环境条件

防护等级	Front IP66
	Front IP67
	Front IP69K
	Terminals IP20

Material Compliance

Conflict Minerals Reporting Template (CMRT)	9AKK108467A5658
REACH Declaration	2CMT2022-006479
RoHS信息	2CMT2022-006498
RoHS状态	Following EU Directive 2011/65/EU and Amendment 2015/863 July 22, 2019
Toxic Substances Control Act - TSCA	2CMT2023-006523
WEEE B2C / B2B	Business To Business
WEEE 类别	5. Small Equipment (No External Dimension More Than 50 cm)

认证及声明（文件编码）

CB认证	CQC_CN_CN50749
CQC认证	CQC2003010305054693
cURus 认证	UL_E496500-20171020
Declaration of Conformity - CCC	2020980305001187
符合性声明 - CE	2CMT2015-005451
Declaration of Conformity - UKCA	2CMT2020-006121
DNV GL Certificate	9AKK107046A3749
EAC认证	RU C-CN.ME77.B.00587/20

包装信息

1级包装单元	bag 10 piece
1级包装宽度	0.125 m
1级包装长度	0.235 m
1级包装高度	0.05 m
1级包装 总重	0.254 kg
1级包装 EAN	7320500381816

分类

对象分类代码	S
ETIM 6	EC001028 - Push button, complete
ETIM 7	EC001028 - Push button, complete
ETIM 8	EC001028 - Push button, complete
e级	V11.0 : 27371228
UNSPSC	39122216

IDEA 粒度分类代码 (IGCC)	5212 >> Push button for distribution board
E-Number (Finland)	2312200
E-Number (Norway)	4372652
E-Number (Sweden)	3717291

分类

低压产品及系统 → 控制产品 → 按钮指示装置 → Compact Range → CP Compact Pushbuttons

