



ENGLISH

Datasheet

RS Pro Manual Ball Valve Stainless Steel 1-1/4in

RS Stock No: **764-4240**



Product Details

RS Pro stainless steel manual ball valve has a screwed end ball for flow control. This ball has 1-1/4 in thread size for external connection. It is available in various sizes.

Features and Benefits

- Full port 1/4 to 4 in (DN8 to DN100)
- W.P: 1000 WOG (PN63)
- W.T: -20 to 200°C
- Blow-out proof stem
- Locking device
- Thread type: ASME B1.20.1 (NPT) DIN2999 and BS21 ISO7/1 and EN10226
- ISO 5211 mounting pad
- Investment casting

**Specifications:**

Attachment Type	Threaded
Ball Material	Stainless Steel
Body Material	Stainless Steel
Handle Colour	Blue
Handle Material	Stainless Steel
Safe for Use With	Gas, Oil, Water
Thread Standard	NPT
Threaded Connection	1-1/4 in NPT
Type	Full Port
Thread Size	1-1/4 in
Maximum Working Pressure	1000 psi
Operating Temperature Range	-20 to +200°C