

# WP-STEEL S 27 - Protective hose



3240864

<https://www.phoenixcontact.com/in/products/3240864>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Protective hose, material: Stainless steel 1.4301/AISI 304, degree of protection: IP40, color: silver, inside diameter: 23 mm, Total length: 10 m

## Commercial data

Item number	3240864
Packing unit	1 m
Minimum order quantity	1 m
Sales key	BF7
Product key	AF7DSA
Catalog page	Page 597 (C-3-2019)
GTIN	4046356738613
Weight per piece (including packing)	3,000 g
Weight per piece (excluding packing)	31,410 g
Customs tariff number	83071000
Country of origin	DE

# WP-STEEL S 27 - Protective hose



3240864

<https://www.phoenixcontact.com/in/products/3240864>

## Technical data

### Notes

Notes on operation	Protective hose length is measured stretched out; length tolerance $\pm 5\%$
--------------------	--

### Product properties

Product type	Protective hose
Tensile strength GRP	500 N

### Dimensions

#### Internal dimensions

Internal diameter	23 mm
-------------------	-------

### Material specifications

Material	Stainless steel 1.4301/AISI 304
Components	halogen-free

### Cable/line

Bending radius, dynamic	120 mm
Bending radius, static	48 mm
Tensile strength	500 N
Halogen-free	yes

### Environmental and real-life conditions

#### Ambient conditions

Degree of protection	IP40
Ambient temperature (operation)	-200 °C ... 600 °C

# WP-STEEL S 27 - Protective hose



3240864

<https://www.phoenixcontact.com/in/products/3240864>

## Classifications

### ECLASS

ECLASS-11.0	27430301
ECLASS-12.0	27430301
ECLASS-13.0	27430301

### ETIM

ETIM 9.0	EC001179
----------	----------

### UNSPSC

UNSPSC 21.0	40141700
-------------	----------

# WP-STEEL S 27 - Protective hose



3240864

<https://www.phoenixcontact.com/in/products/3240864>

## Environmental product compliance

EU RoHS	
Fulfills EU RoHS substance requirements	Yes, No exemptions
China RoHS	
Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits
EU REACH SVHC	
REACH candidate substance (CAS No.)	No substance above 0.1 wt%

# WP-STEEL S 27 - Protective hose



3240864

<https://www.phoenixcontact.com/in/products/3240864>

## Accessories

### WP-SC BRASS 27 - Cable protection end sleeve

3241069

<https://www.phoenixcontact.com/in/products/3241069>



Cable protection end sleeve, material: Brass, nickel-plated, color: silver, inside diameter: 21.5 mm

---

### WP-G BRASS IP40 PG21 - Protective hose screw connection

3241041

<https://www.phoenixcontact.com/in/products/3241041>



Cable gland made from brass with Pg thread, IP40 protection

## WP-STEEL S 27 - Protective hose

3240864

<https://www.phoenixcontact.com/in/products/3240864>



## WP-G BRASS IP40 M25 - Protective hose screw connection

3241048

<https://www.phoenixcontact.com/in/products/3241048>

Cable gland made from brass with metric thread, IP40 protection



---

## WP-GT BRASS PG21 - Protective hose screw connection

3241027

<https://www.phoenixcontact.com/in/products/3241027>

Cable gland made from brass with Pg thread, rotatable, IP40 protection



## WP-STEEL S 27 - Protective hose

3240864

<https://www.phoenixcontact.com/in/products/3240864>



## WP-GT BRASS M25 - Protective hose screw connection

3241034

<https://www.phoenixcontact.com/in/products/3241034>

Cable gland made from brass with metric thread, rotatable, IP40 protection



---

## WP-BASE HF 29 - Hose clamp

3240971

<https://www.phoenixcontact.com/in/products/3240971>

Hose clamp, material: Steel, galvanized, color: black/silver



## WP-STEEL S 27 - Protective hose

3240864

<https://www.phoenixcontact.com/in/products/3240864>



## WP-BASE A PG21 - Protective hose fixing bracket

3241080

<https://www.phoenixcontact.com/in/products/3241080>



Fixing bracket for protective sleeves, fixed with two screws

---

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT (I) Pvt. Ltd.

A-58/2, Okhla Industrial Area, Phase - II, New Delhi-110 020

+91.1275.71420

[info@phoenixcontact.co.in](mailto:info@phoenixcontact.co.in)