

A-1200 ; 0...250 bar gauge; one switching output (PNP)

A-1200 ; 0...250 bar gauge; one switching output (PNP)

Item number: 46967539

Quantity: 1 pcs.

Order code: A-1200-D-BG525-1GI1-3K1HI-M4ZZS-ULZZ
GSA5

W1011A12-ZZPSIOW-

Overview: A-1200 ; 0...250 bar gauge; one switching output (PNP)
Accuracy: 1.0% of span
Measuring range: 0...250 bar gauge
Process connection: G1/4 A ISO1179-2
Sealing: NBR
Permissible medium temperature: -30...+100°C
Output signal: one switching output (PNP)
IO-Link: IO-Link 1.1
Status Indication: Integrated indication
Power supply: 10 ... 32 V DC
Electrical connection: circular connector M12x1, 4-pin
pin assignment: U+=1, U-=3, SP1/C=4
Overload Safety: 2 x
Approvals: cULus
Test protocol: with test protocol
Type of packaging: single packaging
Specifications according to data sheet: PE 81.90

Details: A-1200 ; 0...250 bar gauge; one switching output (PNP)
Accuracy: 1.0% of span
Measuring range: 0...250 bar gauge
Process connection: G1/4 A ISO1179-2
Sealing: NBR
Permissible medium temperature: -30...+100°C
Output signal: one switching output (PNP)
IO-Link: IO-Link 1.1
Status Indication: Integrated indication
Power supply: 10 ... 32 V DC
Electrical connection: circular connector M12x1, 4-pin
pin assignment: U+=1, U-=3, SP1/C=4
Overload Safety: 2 x
Approvals: cULus
Test protocol: with test protocol
Type of packaging: single packaging
Specifications according to data sheet: PE 81.90