



FLAMESTAT JACKET 4965 MFA

ART. NO: 122286

Front placket opening with zip to top of collar and concealed snap fastening / 2 bellowed chest pockets with flap and concealed snap fastening, one with inside D-ring and pen strap, one with opening for radio-antenna at top / 2 loops for monitor and radio / 2 front pockets with zip / Adjustable waist with drawstring / Inside mobile phone pocket / Inside pocket with button / Adjustable cuffs with snap fastening / Extended back / Metal free / Reinforcement at front and back yoke and sleeve ends / Approved according to EN 61482-1-2 APC 1, EN 61482-1-1 ELIM: 7,7 cal/cm² ATPV: 9,3 cal/cm², EN ISO 11612 A1 A2 B1 C1 D3 E3 F1, EN ISO 11611 A1 A2 class 1 (see Flame and welding table for certified garment combinations) / Certified after 50 washes / Leasing laundry-tested according to ISO 15797 / OEKO-TEX® certified.

Material: 60% viscose FR, 20% wool, 10% lyocell, 10% polyamide. Reinforcement 55% viscose FR, 40% wool, 5% polyamide. Inherent flame protection. PFAS free.

Weight: 350 g/m², reinforcement 465 g/m².

Color: F556 Navy/Neon Yellow

Size: XS-3XL



EN 11612



EN 11611



IEC 61482-2



FRISTADS®

SIZES MAY VARY BETWEEN COLORS
Print date: 2025-09-04