

DCMPP569P1-QW

Pruning shears on pole XR 18V 5Ah Li-Ion

5035048838587



Product Description:

Cutting capacity (mm): 38 Height reach (m): 3

Product features and benefits:

- **CUTTING CAPACITY** - Can cut branches with ease and precision up to 38mm thick.
- **BREAKABLE SECTIONS** - Up to 3 meters span, but can still be split into 3 separate sections for easy transport and tidying up.
- **NON-STICK BLADES** - Prevents sap and debris from sticking, saving cleaning time and maximizing productivity.
- **REPLACEABLE BLADE** - Removable with a simple hex screw for sharpening or replacement, ensuring long-lasting durability term.
- **ARTICULATED HEAD** - The 5-position articulating head makes it easy to cut branches, allowing for greater control and precision in hard-to-reach areas.
- **ERGONOMIC HANDLE** - Ensures a comfortable and secure grip, Minimizing fatigue.
- **METAL HOOK** - Perfect for releasing stuck branches, so the work area can be cleared quickly and safely without straining or damaging the tool.

Product Warranty:

This product has a 1-year warranty extended to 3 years after registration

Included Items:

- Pole-mounted pruning shears XR 18V (x1)
- XR 18V 5 Ah DCB184 Battery (x1)
- 4A Charger (x1)

DCMPP569P1-QW

Pruning shears on pole XR 18V 5Ah Li-Ion



5035048838587

Part of the DCMPP569 series

Ref	▲ ▼ Title	▲ ▼
DCMPP569N-XJ	Pruning shears on pole XR 18V	
DCMPP569P1-QW	Pruning shears on pole XR 18V 5Ah Li-Ion	