



230mm x 14 Tpi - 5 pc

METAL: THIN KERF BLADES

- Improved tooth geometry for best speed and double the lifetime.
- Bi-metal quality cutting teeth with 8% cobalt giving the ultimate in performance and lifetime.
- TOUGH NECK™: Stamped indentations around the reception strengthens the blade at its weakest point.
- Slim 0.90 mm thick blade body optimised for maximum speed and flexibility.



Article Number	48475187
Blade length (mm)	230
Materials suited for	Thick metal > 4 mm Medium metal 1.5 - 4 mm Thin metal 0.5 - 3 mm Stainless steel Non ferrous metal (Cu/Al) PVC pipe
Max. cutting capacity metal pipe	ø 10 - 175
Max. cutting capacity non ferrous metals [mm]	3 - 11
Max. cutting capacity stainless steel [mm]	3 - 7
Max. cutting capacity steel (mm)	3 - 11