

FR10 - Modaflame Knit FR Long Sleeve Polo Shirt

Collection: Modaflame™ Knit

Range: Flame Resistant Multi-Norm

Shell Fabric: Modaflame Knit: 60% Modacrylic, 39% Cotton, 1% Carbon Fibre, 200g

Outer Carton: 36



Product information

Convenient for cooler weather and ideal for workers in industries exposed to heat. The stylish design of the garment has a 3-button placket, finished with a ribbed collar and cuffs.

Modaflame™ Knit

Constructed from an inherently fire resistant yarn of 60% Modacrylic, 39% Cotton and 1% Carbon Fibre. Modaflame™ Knit is strong, durable, and highly innovative. The high performance fibres are blended without any chemical treatment giving Modaflame™ Knit it's unparalleled soft, natural touch and appearance.

Flame Resistant Multi-Norm

This industry leading flame resistant range provides multi-standard protection for hazardous environments. These state of the art products are the result of years of experience combined with advanced technology and market research. Commitment to the health, safety and comfort of the wearer can be seen in the wide range of products suitable for all climates and end uses.

Standards

EN ISO 11612 (A1, B1, C1, F1)

EN 1149 -5

IEC 61482-2 IEC 61482-1-1 (ELIM 4.4 CAL/CM², EBT 5.5 CAL/CM²)

IEC 61482-2 IEC 61482-1-2 APC 1

ASTM F1959/F1959M-12 (EBT = 4.3 CAL/CM² (HAF = 66%))

Features

- Inherent flame resistant qualities will not diminish with washing
- Protection against radiant, convective and contact heat
- High cotton content for superior comfort
- Button placket opening
- Ribbed cuffs for added comfort
- Ribbed collar
- Outstanding colour fastness and shrinkage results
- 40+ UPF rated fabric to block 98% of UV rays
- Suitable for use in ESD environments
- Suitable to be worn in an ATEX environment
- CE-CAT III

FR10 - Modaflame Knit FR Long Sleeve Polo Shirt
Commodity Code: 6105201000

Test House

SATRA Technology Europe Ltd (Notified Body No.: NB: 2777)
 Bracetown Business Park
 D15 YN2P, Ireland
 Cert No: 2777/13282-05/E00-00

Wash Care



Carton Dimensions/Weight

Item	Colour	Len	Wid	Hgt	Weight(Kg)	Cubic(m ³)	EAN13	GTIN/DUN14
FR10NARXS	Navy	55.0	36.0	53.0	0.3980	0.1049	5036108243723	25036108732115
FR10NARS	Navy	55.0	36.0	42.0	0.3600	0.0832	5036108161751	25036108625356
FR10NARM	Navy	55.0	36.0	42.0	0.4080	0.0832	5036108161768	25036108625349
FR10NARL	Navy	55.0	36.0	42.0	0.4280	0.0832	5036108161775	25036108625332
FR10NARXL	Navy	55.0	36.0	42.0	0.4360	0.0832	5036108161782	25036108625363
FR10NARXXL	Navy	55.0	36.0	50.0	0.4620	0.0990	5036108161799	25036108625370
FR10NARXXXL	Navy	55.0	36.0	50.0	0.4860	0.0990	5036108161805	25036108625387
FR10NAR4XL	Navy	55.0	36.0	50.0	0.4880	0.0990	5036108217557	25036108704747
FR10NAR5XL	Navy	55.0	36.0	50.0	0.5000	0.0990	5036108217564	25036108704754