

Product datasheet

Specifications



Miniature circuit-breaker (MCB), Acti9 iKQ, 3P, 25A, C curve, 10000A (EN 60898-1)

SE10C325

Main

Range	Acti9
product name	iKQ
Product or component type	Miniature circuit-breaker
Poles description	3P
Number of protected poles	3
[In] rated current	25 A
network type	AC
Trip unit technology	Thermal-magnetic
Curve code	C
Breaking capacity	10000 A Icn at 415 V AC 50/60 Hz conforming to EN 60898-1

Complementary

Network frequency	50/60 Hz
[Ue] rated operational voltage	415 V AC 50/60 Hz
Magnetic tripping limit	5...10 x In
[Ics] rated service breaking capacity	7500 A conforming to EN 60898-1 - 415 V AC 50/60 Hz
Limitation class	3 conforming to EN/IEC 60898-1
[Ui] rated insulation voltage	440 V AC 50/60 Hz conforming to EN/IEC 60898-1
[Uimp] rated impulse withstand voltage	4 kV conforming to EN/IEC 60898-1
Contact position indicator	Yes
control type	Toggle
local signalling	Trip indicator
Mounting mode	Plug-on
Mounting support	Rail
9 mm pitches	6
Height	85 mm
Width	54 mm
Depth	78.5 mm
Net weight	0.362 kg
Colour	White
Mechanical durability	20000 cycles

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Electrical durability	10000 cycles
Connections - terminals	Single terminal (bottom) 1...25 mm² rigid Single terminal (bottom) 1...16 mm² flexible
Wire stripping length	14 mm for bottom connection
Tightening torque	2 N.m bottom
Earth-leakage protection	Without

Environment

Standards	EN/IEC 60898-1
IP degree of protection	IP20 conforming to IEC 60529
Pollution degree	2 conforming to EN/IEC 60898-1
overvoltage category	III

Packing Units

Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	5.4 cm
Package 1 Width	8.2 cm
Package 1 Length	9.5 cm
Package 1 Weight	387.4 g
Unit Type of Package 2	BB1
Number of Units in Package 2	4
Package 2 Height	9.5 cm
Package 2 Width	10.2 cm
Package 2 Length	24 cm
Package 2 Weight	1.617 kg
Unit Type of Package 3	S03
Number of Units in Package 3	32
Package 3 Height	30 cm
Package 3 Width	30 cm
Package 3 Length	40 cm
Package 3 Weight	13.36 kg

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

[Environmental Data explained >](#)

[How we assess product sustainability >](#)

Use Better

 Materials and Substances	
Packaging made with recycled cardboard	No
Packaging without single use plastic	No
EU RoHS Directive	Compliant
SCIP Number	26ff71d1-98cf-4280-8725-455b9a6b2fb9
REACH Regulation	REACH Declaration
China RoHS Regulation	China RoHS declaration

Use Again

 Repack and remanufacture	
WEEE	 The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins
Take-back	No