

Connecting cable NEBC-M12G5-S-1,5-N-M12G5

Part number: 8085741

FESTO



 [General operating condition](#)

Data sheet

Feature	Value
Cable designation	With accessories
Frequency of connection	500
Product weight	163 g
Electrical connection 1, function	Field device side
Electrical connection 1, design	Round
Electrical connection 1, connection type	Plugs
Electrical connection 1, cable outlet	Straight
Electrical connection 1, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 1, number of connections/cores	5
Electrical connection 1, used connections/cores	5
Electrical connection 1, type of mounting	Screw-type lock
Electrical connection 1, connection pattern	00995383
Electrical connection 2, function	Controller side
Electrical connection 2, design	Round
Electrical connection 2, connection type	Plugs
Electrical connection 2, cable outlet	Straight
Electrical connection 2, connector system	M12x1, A-coded to EN 61076-2-101
Electrical connection 2, number of connections/cores	5
Electrical connection 2, used connections/cores	5
electrical connection 2, type of mounting	Screw-type lock
Electrical connection 2, connection pattern	00995383
Operational voltage range DC	0 V ... 30 V
Operational voltage range AC	0 V ... 30 V
Current rating at 40° C	4 A
Immunity to surge	0.8 kV
Shielding	yes
Cable length	1.5 m
Cable characteristic	Standard
Test conditions cable	Test conditions on request
Cable diameter	5 mm
Cable structure	4 x 0.34 mm ²
Nominal cross section conductor	0.34 mm ²
Degree of protection	IP65 IP67
Note on degree of protection	In assembled state
Ambient temperature	-25 °C ... 70 °C

Feature	Value
Ambient temperature with moving cable	-5 °C ... 70 °C
CE mark (see declaration of conformity)	In accordance with EU RoHS Directive
UKCA marking (see declaration of conformity)	To UK RoHS instructions
LABS (PWIS) conformity	VDMA24364-B2-L
Note on materials	RoHS-compliant
Pollution degree	3
Corrosion resistance class CRC	2 - Moderate corrosion stress
Material cable sheath	TPE-U(PUR)
Cable sheath colour	Light grey
Material housing	TPE-U(PUR)
Housing colour	Black
Material screw-type lock	Nickel-plated brass
Material electrical contact	Gold-plated bronze Gold-plated brass
Material insulating sheath	PVC