Disclaimer. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications



SELECTOR SWITCH OPERATOR 30MM T-K

Local distributor code: 387207199

9001KS43FB

EAN Code: 3389118039698

Main

Range of product	Harmony 9001K		
Product or component type	Head for selector switch		
Device short name	9001K		
Type of operator	stay put		
Operator profile	Black long handle		

Complementary

Bezel material	Metal
Mounting diameter	30 mm
Net weight	0.172 kg
Shape of signaling unit head	Octagonal
Operator position information	3 positions
Contacts type and composition	Without contact block
Mechanical durability	500000 cycles
Product compatibility	9001KA1, mounted side 1
Device presentation	Basic element
Cap/operator or lens colour	Black
Operator profile	Long handle
Type of operator	Stay put
Size	30 mm
Cam profile	3

Environment

Protective treatment	TC	
Ambient air temperature for storage	-4070 °C	
Ambient air temperature for operation	-2570 °C	
Overvoltage category	Class II conforming to IEC 61140	
IP degree of protection	IP66 conforming to IEC 60529	

NEMA degree of protection	NEMA 1 NEMA 12 NEMA 13 NEMA 2 NEMA 3 NEMA 3 NEMA 3R NEMA 4		
Standards	CSA C22.2 No 14 IEC 60947-5-1 JIS C 4520 IEC 60947-5-4 UL 508 IEC 60947-1 JIS C 852		
Product certifications	UL 508 NEMA		
Vibration resistance	7 gn (f= 2500 Hz) conforming to IEC 60068-2-6		
Shock resistance	50 gn conforming to IEC 60068-2-27		

Packing Units

_	
Unit Type of Package 1	PCE
Number of Units in Package 1	1
Package 1 Height	4.500 cm
Package 1 Width	4.700 cm
Package 1 Length	9.400 cm
Package 1 Weight	117.000 g
Unit Type of Package 2	S01
Number of Units in Package 2	24
Package 2 Height	15.000 cm
Package 2 Width	15.000 cm
Package 2 Length	40.000 cm
Package 2 Weight	3.012 kg

Logistical informations

Country of origin FR

Contractual warranty

Warranty 18 months



Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing "Use Better, Use Longer, Use Again" campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better


Packaging made with recycled cardboard	Yes
Packaging without single use plastic	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope)
SCIP Number	Ae0c4eb9-0bfb-40a4-851f-5c619fbe777d
REACh Regulation	REACh Declaration


Use Again

○ Repack and remanufacture				
Take-back	No			
WEEE Label	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins			

Dimensions Drawings

Dimensions






 \boldsymbol{e} panel thickness: 1 to 6 mm / 0.04 to 0.24 in.

9001KS43FB

Mounting and Clearance

Contact Block Mounting Position


Top and Rear views



- (1) It is possible to mount up to 3 levels of contacts blocks (maximum of 6 contacts blocks)
- (2) Operator
- (3) Locating notch
- (4) Side 1
- (5) Side 2

Panel Cut-Out


Clearance




Legend plate	a min.		b min.	
	mm	in.	mm	in.
9001KN2••	57.2	2.25	44.5	1.75
9001KN3••	57.2	2.25	50.8	2.00

Individual Cut-outs Details

2 alternatives





Offer Marketing Illustration

Product benefits / Features



Offer Marketing Illustration

Product benefits / Features

Technical Benefits

Harmony 9001K

