

ROLINE USB4 Gen3x2 Cable, with Emark, C-C, M/M, 8K UHD-2, 40Gbit/s, 240W, white, 1 m

Product No.	11.02.8340	
Manufacturer	ROLINE	
Manufacturer No.	11.02.8340	
EAN (single piece)	7630049632790	



USB4 Gen 3x2 Cable in very high quality with the reversible USB-C plug at both ends for data transfer rates of up to 40 Gbit/s and USB Power Delivery up to 48V / 5A (240 W). Cable jacket made of white textile braiding to perfectly fit the design of the Apple iPhone 15 products.

- High quality USB4 Gen 3x2 cable with improved shielding
- With the reversible Type C connectors at both ends
- Gold-plated contacts for low wear at high plugging cycles
- Suitable for data transfer rates of up to 40 Gbit/s
- Supports USB Power Delivery to 48V / 5A

The major benefits of the USB4 includes faster transfer speeds (up to 40 Gbit/s), a better management of video bandwidth (using a process called "protocol tunneling" that sends DisplayPort, PCIe and USB packets at the same time while allocating bandwidth accordingly) and optional compatibility with Thunderbolt 3 products.

Technical specifications	
Manufacturer	ROLINE
Product group	Cable
Product type	USB4 Cable
Colour	white
Length	1 m

Transfer quality	USB4 Gen3x2 40 Gbit/s
Connection ports	USB Type C (USB-C) Male / USB Type C (USB-C) Male
Side 1 Connector Type	USB Type C (USB-C)
Side 1 Connector Gender	Male
Side 2 Connector Type	USB Type C (USB-C)
Side 2 Connector Gender	Male
Max. resolution	7680 x 4320 @60Hz (8K, UHD-2)
Maximum data transfer rate	40 Gbit/s
Area of application	External
Supported charging technology	USB-PD - USB Power Delivery
Power (max.)	240 W
Cable shielding	Screened
Hand locking screws	no
Weight	53 g
Height of packaging (single piece)	20 mm
Width of packaging (single piece)	100 mm
Depth of packaging (single piece)	100 mm
Package weight (single piece)	0.07 kg