



SOCKET SETS



S106



- 1/4" and 1/2" sockets, and combination spanners set
- High performance alloy steel
- Matt finish
- ISO 1174
- DIN 3120
- Case: High Density Polythene (HDPE)
- Contents, 106 pcs

- 12 pcs 1/4" hex sockets:
4, 4.5, 5, 5.5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- 10 pcs 1/4" hex deep sockets:
4, 5, 6, 7, 8, 9, 10, 11, 12, 13 mm
- 15 pcs 1/2" hex sockets:
10, 12, 13, 14, 15, 16, 17, 18, 20, 21, 23, 24, 27, 32, 34 mm
- 9 pcs hex sockets AF:
3/8 7/16 (11) 1/2 9/16 11/16 3/4 (19) 13/16 7/8 (22) 1-3/16"
- 4 pcs 1/2" hex impact sockets: 17, 19, 21, 24 mm
- 4 pcs 1/4" socket drivers Phillips PH 1, 2, 3, 4
- 3 pcs 1/4" socket drivers slotted 4, 5.5, 7 mm
- 6 pcs 1/4" socket drivers hex 3, 4, 5, 6, 8 10 mm
- 3 pcs 1/4" socket drivers Pozidriv PZ 1, 2, 3
- 8 pcs 1/4" socket drivers Torx® T 8, 10, 15, 20, 25, 27, 30, 40
- 2 pcs 1/4" extension bars 50 mm / 2" & 100 mm / 4"
- 1 pc 1/4" sliding T-bar 100 mm / 4"
- 1 pc 1/4" universal joint
- 1 pc 1/4" spinner with 2-component handle
- 2 pcs 1/2" extension bars 125 mm / 5" & 250 mm / 10"
- 1 pc 1/2" universal joint
- 1 pc 1/2" spark plug socket hex 21 mm (13/16")
- 1 pc 1/2" T-adapter
- 3 pcs L-Keys hex 1.5, 2, 2.5 mm
- 1 pc 1/4" ratchet, 60 teeth / 6° action angle, quick release
- 1 pc 1/2" ratchet, 60 teeth / 6° action angle, quick release
- 4 pcs flex head spanners 8-9, 10-11, 12-13, 14-15 mm
- 13 pcs combination spanners 7, 8, 9, 10, 11, 12, 13, 14, 15, 16, 17, 18, 19 mm,
on a practical removable tool-rack
- 1 pce removable three section plastic box with lid

RS 361-3148