



ENGLISH

Datasheet

Stock No: 235-7437

RS Pro PVC Blue Flexible Tube 10m Long Reinforced



Product Details

Layflat Hose

Manufactured from PVC and synthetic fibres

Good chemical resistance

Easily rolls up after use

Temperature range -25 to +60°C

Note

This data refers to performance at 18°C. Any changes in temperature will affect the performance data

* May be supplied in grey



ENGLISH

Specifications:

Inner Diameter	38mm
Outer Diameter	43.2mm
Material	PVC
Colour	Blue
Reinforced	Yes
Suitable Applications	Chemical, Water
Length	10m
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+60°C
Maximum Working Pressure	5 bar
Operating Temperature Range	-25 to +60 °C