

# BCC A335-0000-20-000-71X5A5-000

Order Code: BCC070L











Pacie	footures
Dasic	features

Approval/Conformity CE cURus EAC WEEE

**Electrical connection** Cable diameter D 10...12 mm Connection 7/8"-16 UN-Male, Straight, 5-pin Number of connectable contacts 5 System Can be fabricated **Electrical data** 

600 VDC / 600 VAC Operating voltage Ub Rated current (40 °C) 9.0 A

### **Environmental conditions**

Ambient temperature -25...85 °C IP rating IP67

### Material

Material contact carrier PUR, PA Material contacts Brass Material cover nut Die-cast zinc Material grip PBT

### Mechanical data

Connection cross-section 0.14...1.5 mm<sup>2</sup> Tightening torque pigtail 1.5 Nm Type of wire mounting Screw terminals

#### Remarks

Enclosure rating per IEC 60529, only in screwed state with the associated mating piece.

## **Connector Drawings**



PIN 1-5 usable