

Professionally approved products.

Screwdriver Sets

7 Pc Precision Screwdriver Set



[RS Stock No. 243-513](#)



Material

Screwdriver blades: Silicone Chrome Molybdenum Vanadium steel (svcm55)

Handles: Polypropylene / TPR double injection

Finish

Screwdriver blades: Satin chrome finish with Phosphate black tip

Handle: black colour TPR grip and red colour (pantone - 187c) injection handle.

Hardness

Screwdriver blades: Heat treated to HRC: 55~59 degrees

Contents:

7 pc - Precision screwdrivers with black colour TPR grip and red Phosphate injection handle (remove the magnet from steel blade, handle style - j3000)

Slotted: 1.50 x 0.23 x 60 mm,

2.5 x 0.4 x 60 mm,

3.0 x 0.5 x 60 mm

3.0 x 0.5 x 100 mm

Phillips: No.00 x 60 mm,

No.0 x 60 mm

No.1 x 80 mm

Remarks:. Torque, dimensions and gauge tests meet din 8320 & din-iso 2380-1 standard.

Type tip and din-iso 8764 ph standard

Features

1. High grade silicone chrome Molybdenum Vanadium Steel bar for high torque
2. Anti-slip soft material for optimum & comfort grip
3. Rotating cap allow use to drive easy & adjust precisely