

MFC SERIES - ACTIVATED CARBON FILTER

MFCC - Replacement cartridge for regular MFC - Activated carbon filtration



Part number	Flow rate at 7 bar (m ³ /h) (ΔP= 0,08 bar)	Temperature min/max (°C)	Max. operating pressure (bar)
MFCC 5532	55	5 / 50	20
MFCC 7040	70	5 / 50	20
MFCC 10060	100	5 / 50	20
MFCC 15090	150	5 / 50	20
MFCC 225130	225	5 / 50	20
MFCC 300175	300	5 / 50	20
MFCC 400235	400	5 / 50	20
MFCC 500295	500	5 / 50	20
MFCC 800470	800	5 / 50	20
MFCC 1550910	1.550	5 / 50	20