

SKINDICHT® SE-M

SKINDICHT® SE-M, angular cable outlet, incised sealing ring as a seal, for missing connection thread and high mechanical load



Temperature-resistant



Connector with standard housing unit



Space requirement



Mechanical resistance



Corrosion-resistant

Benefits

Sealed by incised sealing ring

Corrosion-resistant

Easy to install

Completely safe cable entry

Low overall height

Application range

For high mechanical stress

When no connection thread is provided

Product Make-up

M20 x 1.5 - M25 x 1.5 with 2 screw holes

M32 x 1.5 with 4 screw holes

With incised sealing ring

Last Update (11.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.

PN 0456 / 02_03.16

SKINDICHT® SE-M**Note**

Drawing on request

Technical Data

Classification:	ETIM 5.0 Class-ID: EC000441 ETIM 5.0 Class-Description: Cable screw gland
Material:	Body: zinc die-casting, grey, hammer tone finish Compression screw: nickel-plated brass Incised sealing ring: CR/NBR O-ring: NBR
Protection rating:	IP 55
Temperature range:	-20°C to +80°C

Note

Photographs are not to scale and do not represent detailed images of the respective products.
Prices are net prices without VAT and surcharges. Sale to business customers only.



SKINDICHT® SE-M

Article number	Article designation / size	Incised sealing ring ØF (mm)	Overall height (mm)	SW mm	Total length C (mm)	Overall width (mm)
SKINDICHT® SE-M						
52108000	M 20 x 1,5	4/7/10/13	31	20	49.2	42
52108010	M 25 x 1,5	8.5/11.5/14.5/17.5	40	25	68.2	60
52108020	M 32 x 1,5	16/19/22/25	51.5	32	84.2	66

Last Update (11.07.2017)

©2017 Lapp Group - Technical changes reserved

Product Management www.lappkabel.de

You can find the current technical data in the corresponding data sheet.
PN 0456 / 02_03.16