Datasheet

R-F1BR100400000 Datasheet

ENGLISH

POSITIONS	02 PIN	03 PIN	04 PIN	05 PIN	06 PIN	07 PIN	08 PIN	10 PIN	14 PIN	16 PIN
VIEW FROE TERMINATION SIDE SOCKET PART										

NOTE:

1. MATERIAL AND FINISH

1.1. SHELL ASSEMBLY: COPPER ALLOY,OUTER SHELL AND COLLET NUT Cr PLATING,OTHER METALLIC COMPONENTS Ni PLATING

1.2. INSULATOR: PEEK

1.3. CONTACT: COPPER ALLOY, GOLD PLATING

2. RoHS COMPLIANCE

3. PART NO.

No. OF CONTACTS	øC	L
02,03.....07,08	0.7	3.0
10,14,16	0.5	4.0

CONTACT POS.
02-16=2pin-16pin

SHELL MATERIAL
0=Brass

CODE	KEY ANGLES
0	0
A	30°
B	60°
"	"

CODE	CONTACT TYPE
2	Male Solder Contact
4	Female Solder Contact
1	Male Print Contact
3	Female Print Contact
M	Crimp Female Contact 
C	Crimp Male Contact



PANEL CUT-OUT

REV.	DESCRIPTION	DATE	APPD
X2	UPDATE RELEASE	7/15'15	Seawen

UNITS ■mm □INCH		
GENERAL TOLERANCES: (UNLESS SPECIFIED)	mm	INCH
4 PLACE	± **	±. **
3 PLACE	± 0.10	±. **
2 PLACE	± 0.30	±. **
1 PLACE	± 0.50	±. **
ANGULAR:	X°± 2°	X°±**

NAME: SNAP LATCH METAL 1B FIXED SOCKET NUT FIXING

APPD: Seawen 7/15'15

CHKD: Peter 7/15'15

DRAWN: Alex 7/15'15

TITLE: CUSTOMER DWG.

DWG NO: 010-0000-B26 C

SCALE:	SHEET:	REV.:
2.5/1	1/4	X2

A1

1B FIXED SOCKET SOLDER CONTACT TYPE VIEW



1B FIXED SOCKET PRINT CONTACT TYPE VIEW



1B FIXED SOCKET CRIMP CONTACT TYPE VIEW



REV.	DESCRIPTION	DATE	APPD
X2	UPDATE RELEASE	7/15'15	Seawen

UNITS ■mm □INCH		
GENERAL TOLERANCES: (UNLESS SPECIFIED)	mm	INCH
4 PLACE	± **	±. **
3 PLACE	± 0.10	±. **
2 PLACE	± 0.30	±. **
1 PLACE	± 0.50	±. **
ANGULAR:	X°± 2°	.X°± **

NAME: SNAP LATCH METAL 1B FIXED SOCKET NUT FIXING

APPD: Seawen 7/15'15

CHKD: Peter 7/15'15

DRAWN: Alex 7/15'15

TITLE: CUSTOMER DWG.

DWG NO: 010-0000-B26 C

SCALE:	SHEET:	REV.:
2.5/1	2/4	X2

A1

PCB DRILLING PATTERN:

02PIN



03PIN



04PIN



05PIN



06PIN



07PIN



08PIN



10PIN



14PIN



16PIN



REV.	DESCRIPTION	DATE	APPD
X2	UPDATE RELEASE	7/15'15	Seawen

UNITS ■mm □INCH

GENERAL TOLERANCES: (UNLESS SPECIFIED)

	mm	INCH
4 PLACE	± **	±. **
3 PLACE	± 0.10	±. **
2 PLACE	± 0.30	±. **
1 PLACE	± 0.50	±. **
ANGULAR:	X°± 2°	.X°± **

NAME: SNAP LATCH METAL 1B FIXED SOCKET NUT FIXING

APPD: Seawen 7/15'15

CHKD: Peter 7/15'15

DRAWN: Alex 7/15'15

TITLE: CUSTOMER DWG.

DWG NO: 010-0000-B26 C

SCALE:	SHEET:	REV.:
2.5/1	3/4	X2

A1

KEY ANGLES (RECEPTACLE FRONT VIEW)



REV.	DESCRIPTION	DATE	APPD
X2	UPDATE RELEASE	7/15/15	Seawen

UNITS ■mm □INCH		
GENERAL TOLERANCES (UNLESS SPECIFIED)	mm	INCH
4 PLACE	± **	±.**
3 PLACE	± 0.10	±.**
2 PLACE	± 0.30	±.**
1 PLACE	± 0.50	±.**
ANGULAR	X°± 2°	.X°±**

NAME: SNAP LATCH METAL 1B FIXED SOCKET NUT FIXING

APPD: Seawen 7/15/15

CHKD: Peter 7/15/15

DRAWN: Alex 7/15/15

TITLE: CUSTOMER DWG.

DWG NO: 010-0000-B26 C

SCALE	SHEET	REV.
2.5/1	4/4	X2

A1