

Specifications

Photo is representative



Eaton 17.5CAV2

VT fuse-link, medium voltage, 2 A, AC 17.5 kV, 220 x 41.3 mm, back-up, IEC

General Specifications

PRODUCT NAME	Eaton Bussmann series medium auxiliary fuse
CATALOG NUMBER	17.5CAV2
PRODUCT LENGTH/DEPTH	220 mm
PRODUCT HEIGHT	41.3 mm
PRODUCT WIDTH	41.3 mm
PRODUCT WEIGHT	700 g
CERTIFICATIONS	IEC60282-1
EAN	5027590438018
UPC	051712831871

Electrical data

AMPERAGE RATING	2 A
VOLTAGE RATING	17.5 kV
BREAKING CAPACITY	40 kA
PERFORMANCE CAT ACCORDING TO IEC 60282-1	Back-up
CLASS	Class back-up
RESISTANCE	1.69 ohms

Product specifications

APPLICATION	Protection of auxiliary transformers
FUSE INDICATOR	Non Indicating
FUSE SIZE	220 x 41.3 mm
STANDARD	IEC

Resources

	eaton-bussmann-circuit-protection-brochures-en.pdf
BROCHURES	eaton-bussmann-series-product-range-overview-brochure-br134002en-en-us.pdf
MCAD MODEL	eaton-mv-potential-transformer-gen-purp-fuses-mcad-3d-models-17-5cav.stp

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Follow us on social media to get the latest product and support information.

