



Datasheet

ENGLISH


RS PRO SP29 Series, Socket Panel Mount Connectors



The RS PRO SP29 series is a range of lightweight, robust waterproof connectors which are sealed to IP68. Threaded coupling ensures a secure connection, even in the harshest environments. These products are ideal for use in outdoor applications where secure, waterproof connection is required.

Features and Benefits

- Threaded Coupling
- 400 V to 500 V rating
- IP68
- 2-26 Poles
- Socket Connections



Number of Contacts

Number of contact	2	3	4	7	8	9	10	108	12	16	17	20	24	26
Male contact face view	(1)	①	(<u>;</u>)											
Rated current (A)	50	50	25	25	25	25 5	25	10	10	10	10	5	5	5
Contact diameter(mm)	3.5	3.5	2.5	2.5	2.5	#2.5X4 #1 X 5	2.5	1.5	1.5	1.5	1.5	1	1	1
Rated voltage (AC.V)	500	500	500	500	500	500	500	500	500	500	500	400	400	400
Test voltage(AC.V) 1 min	1500	1500	1500	1500	1500	1500	1500	1500	1500	1500	1500	1200	1200	1200
Contact resistance (m Ω)	0.5	0.5	1	1	1	5	1	2.5	2.5	2.5	2.5	5	5	5
Termination	solder / screw	solder/seres	solder/sores	polder/screw	solder screw	solder	solder/sorew	solder	solder	solder	solder	solder	solder	solder
Wire size for solder (mm ¹ /AWG)	≤10/7	≤10/7	≤4/11	≤4/11	≤4/11	<8/11	≤4/11	≤2/14	≤2/14	≤2/14	≤2/14	<0.785/18	<0.785/18	10.765/18
Wire size for screw termination (mm ² /AWG)	<6/10	<6/10	≤1.5/15	≤ 1.5/15	≤1.5/15	1	≤1.5/15	1	1	1	1	1	1	1