

## Han EMC/B 10 Protection Cover metal



Image is for illustration purposes only. Please refer to product description.

Part number	09 62 810 5425
Specification	Han EMC/B 10 Protection Cover metal
HARTING eCatalogue	<a href="https://harting.com/09628105425">https://harting.com/09628105425</a>

### Identification

Category	Accessories
Series of hoods/housings	Han <sup>®</sup> EMC/B
Type of accessory	Protection cover
Description of the accessory	for bulkhead mounted housings for surface mounted housings With fixing cord

### Version

Size	10 B
Locking type	Double locking lever
Details	Not suitable for housings with external seals.

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP65
Type rating acc. to UL 50 / UL 50E	4 12

### Material properties

Material (hood/housing)	Aluminium die-cast
Surface (hood/housing)	Uncoated
Colour (hood/housing)	Unpainted
RoHS	compliant
ELV status	compliant



**Pushing Performance**  
Since 1945

## Material properties

China RoHS	e
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076 CSA-C22.2 No. 182.3 ECBT8.E235076
Approvals	DNV GL

## Commercial data

Packaging size	1
Net weight	50.998 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140191907
eCl@ss	27440208 Cap for industrial connectors
ETIM	EC002314
UNSPSC 24.0	39121467