

Main

Range of product	Mureva Styl
Range	Mureva Styl
Product or component type	Rocker
Number of rocker	1
Colour tint	White (RAL 9003)

Complementary

Device mounting	Surface Flush
Actuator	Rocker
Condition of use	Indoor/outdoor
Material	ABS (acrylonitrile butadiene-styrene) PC (polycarbonate) PP (polypropylene)
IP degree of protection	IP55
IK degree of protection	IK08
Width	70 mm
Height	70 mm
Chemical and detergent products resistance	Resistant to alcohol (70 %) Resistant to alcohol (96 %) Resistant to A-Lactic Acid Resistant to diluted quaternary ammonium Resistant to diluted bleach Resistant to diluted ammonia Resistant to soapy water Resistant to crystal cleaner Resistant to hydrogen peroxide 10 volumes Resistant to hexane
Depth	14 mm

Environment

Quality labels	NF CE EAC AENOR
Flame retardance	Self-extinguishing 650 °C conforming to IEC 60695-2-1
Standards	EN 60669-1
Ambient air temperature for operation	-5...40 °C
Ambient air temperature for storage	-25...55 °C

The information provided in this documentation contains general descriptions and/or technical characteristics of the products of the Schneider Electric group. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Offer Sustainability

REACH Regulation	REACH Declaration
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Toxic heavy metal free	Yes
Mercury free	Yes
Sustainable packaging	Yes
RoHS exemption information	Yes
China RoHS Regulation	China RoHS Declaration