



Outlet filter, Extract: W: 223 mm, H: 223 mm, RAL 7035, IP54, EMC

Model			
product brand name	SIVACON		
product designation	outlet filter		
type of ventilation	ventilation		
fan design withdrawable fan	No		
design of the product EMC version	Yes		
General technical data			
cutout width	223 mm		
cutout height	223 mm		
Protection class			
protection class IP	IP54		
Appearance			
color	light grey		
Product details			
product component fan	No		
Mechanical Design			
height	250 mm		
width	250 mm		
depth	37 mm		
installation location	Control cabinet...panels, door		
fastening method	screw fixing		
fastening method			
• 19-inch installation			No
• wall mounting			Yes
net weight	0.6 kg		
material	plastic		
ambient temperature during operation			
• minimum			-20 °C
• maximum			65 °C
Approvals Certificates			
General Product Approval		other	Environment



[Confirmation](#)

[Miscellaneous](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging
<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8MR6400-6GV45>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8MR6400-6GV45>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8MR6400-6GV45

CAX-Online-Generator

<http://www.siemens.com/cax>

Tender specifications

<http://www.siemens.com/specifications>

last modified:

5/24/2025 

