

Item code

CDSHM 42



Brief description:

male insert, 42 poles, Spring connection contacts SQUICH, 10A, 400V, silver plated, size "104.27", CLASS inserts

Product description		Approvals / Standards	
Model	male insert	Reference standard	EN 61984 (2001-11)
Version	Spring connection contacts SQUICH	Quality mark	  EAC
Series	CDSH	Conformity	CQC, CE
Product type	with male contacts	General ordering information	
Family	CLASS inserts	EAN code	8015747222631
Size	size "104.27"	Tariff number	85369095
N° of poles	42 poles + 	Packaging Information	
Technical data		Packaging length	245,00 mm
Current	10 A (A.C. and D.C.)	Packaging height	165,00 mm
Voltage	400 V	Packaging width	215,00 mm
Sustained impulse voltage	6kV	Packaging weight	3,83 kg
Pollution degree	3	Packaging volume	8,69 dm ³
Wire section	0,14 mm ² - 2,50 mm ²	Packaging description	Carton box
AWG size	26 - 14	Packaging quantity	30 Pcs
Operating temperature range (min, max)	-40°C ... +125°C	Packaging EAN code	8015747222815
Contact type	silver plated	Sub-packaging length	197,00 mm
Plugging cycles	≥ 500	Sub-packaging height	55,00 mm
IP degree of protection	IP20 without enclosure; IP65/IP66/IP67/IP68 with enclosure	Sub-packaging width	113,00 mm
Wire cross section PE	0,14 - 4 mm ² ; AWG 20 - 12	Sub-packaging weight	0,64 kg
Other technical details		Sub-packaging volume	1,22 dm ³
Insulation resistance	≥ 10 GΩ	Sub-packaging description	Carton
Weight	127,67 g	Sub-packaging quantity	5 Pcs
		Sub-packaging EAN barcode	8015747222822



Item code

CDSHM 42



Notes

actuator button connections



Reopening