

7418-04

Rectangular reversible ratchet head

14x18

Code	ETIM
7687660	EC002218
EAN	UNSPSC
4002805748046	27-11-17-11
Country of origin	eCl@ss
Germany	21-04-02-08
Customs tariff number	
82079099	



Article description

- For solving difficult assembly problems, easily replaceable
- Forged
- Chromium vanadium steel
- Matt chrome-plated
- With locking pin
- Fine-toothed
- Return angle 7°
- Max. continuous load of ratchet according to DIN EN ISO 6789 and/or maximum load of cavity

Article information

Contents (Qty of pieces)	1	Number of teeth	50
Net weight [kg]	0,79 kg	Continuous load	3/4" = 400 N·m
Total width [mm]	64 mm	Depth gauge [metric]	33,0 mm
Material	Chrome-vanadium steel	Head height 2 [mm]	35,5 mm
Drive connector square (male)	3/4"	Drive connector rectangular	14 x 18 mm
Drive connector square (male)	20 mm	Head height 1 [mm]	35,5 mm
Return angle	7,2°	Width of head 1 [mm]	64,0 mm