

Eaton EBH00013TTM8

Catalog Number: EBH00013TTM8

Eaton Bussmann series low voltage NH fuse base, Switch disconnecter, low voltage, 160 A, AC 690 V, NH000, AC21B, 3P, IEC, 60mm busbar, cable terminal – top, for connection of conductors with lug terminals - M8 screws



General specifications

Product Name	Catalog Number
Eaton Bussmann series low voltage NH fuse base	EBH00013TTM8
	EAN
	5027590334914
Product Length/Depth	Product Height
195 mm	145 mm
Product Width	Product Weight
100 mm	921 g
Compliances	Certifications
CE	IEC/EN 60947-1
	IEC 60947-3

Product specifications

Type

Fuse accessory

Application

Motor control centres, distribution boards, Cable distribution cabinets

Amperage Rating

160 A

Rated operational power at AC-23A, 400 V, 50 Hz

0.064 kW

Rated permanent current (Iu)

160 A

Rated uninterrupted current (Iu)

160 A

Conditioned rated short-circuit current Iq

0.1 kA

With error protection

No

Number of poles

Three-pole

Rated operation power at AC-23, 400 V

0.064 kW

Rated short-time withstand current (Icw)

100 kA

Electrical connection type of main circuit

Screw connection

Actuator position

Front side

Actuator type

Cover grip

Construction size

NH000

Fuse shape

Horizontal

Suitable for

Busbar mounting

Resources

Catalogs

CA134002EN

[eaton-product-overview-for-machinery-catalogue-ca08103003zen-en-us.pdf](#)

Declarations of conformity

[CE fuse switch disconnectors, EBC, EBV and EBH series](#)

[UKCA fuse switch disconnectors, EBC, EBV and EBH series](#)

Technical data sheets

[10275 EBV Vertical fuse switch-disconnector](#)

[10292 EBH000 Horizontal switch-disconnector](#)

Technical service bulletins

[10293 EBH Horizontal switch-disconnector](#)

NH000

Suitable for fuses

NH000

Cable entry type

Other

Mounting method

DIN rail

60 mm busbar mounting

Voltage rating

690

Degree of protection (front side)

IP30

Electrical connection type

Screw connection

Rated operating voltage (Ue) at AC - max

690 V



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia