



ENGLISH

Datasheet

RS 4 Core Unscreened Industrial Cable, PVC Sheath, 6.7mm OD, 0.5 mm² CSA 2.5 A, 440 V, 25m

Stock Number - 660-7067



Description:

Rated Temperature (oC): -20 ~ 80

Rated Voltage (V):440

Flammability Test: IEC60332-1



ENGLISH

Construction:

Conductor: Tinned Copper

Conductor Dia. (mm): 0.20 ± 0.008 x 16

Insulation: PVC

Insulation Dia. (mm): 1.8 ± 0.05 x 4C

Tape: Mylar Spiral

Coverage: $\geq 115\%$

ID Thread : Green, White/Green

A rip cord : 210 D

Jacket: FR-PVC

Outer Dia. (mm): 6.3 ± 0.1

Colour:

The colour of the insulation: Red , Blue , Green , Yellow

The jacket colour: Black

Marking(3times/m):

RS 6607067 16 - 2 – 4A

Electrical Characteristics:

Max.Conductor DC Resistance at 20°C (Ω /Km) :
<40

Min.Insulation DC Resistance at 20°C ($M\Omega$ *KM) :
>200

Current Rating : 2.5 A

