



## BOX OF SERIES S1 IMPACT WRENCHES 1/2"

**RC2780BC**

### SAM Outillage

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

Photos and texts not contractually binding. Do not litter. Document generated on 2025-07-18 15:12:38





**DESCRIPTION**

**BOX OF SERIES S1 IMPACT WRENCHES 1/2"**

**POWERFUL**

The performance of its so-called "cold" motor develops optimum power of 1,350 Nm when full-power unscrewing is required. The power developed represents an improvement of at least 25% with respect to what commonly exists for 1/2" wrenches. Intensive-use compact wrench for maintenance jobs, and also for automotive applications: exhaust, power-train... Low-consumption wrench. Double-hammer punch, reducing the vibrations. Cold-insulating S1 casing (handhold and wrench balancing...). 3-Position variable torque control and sensitive-touch control button at the front. Suspension ring.

**SPECIFIC DATA**

Designation	IMPACT WRENCH 1/2" BOX
Sales reference	RC2780BC

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France  
RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-  
<https://www.sam-outillage.com/>



L (mm)	193
Weight (g)	2000
Rotation speed (rpm)	10 000
Vibration (m/s <sup>2</sup> )	5,4
Noise level (dBa)	85 / 93,7
C mm	6,3
C min mm	400
C mm	1/4
Maximum input torque Nm	1 350
Hammer type	
Guarantee	M2   SAM Equipment and Machine Guarantee

**Guarantee applied**

**M2 | SAM Equipment and Machine Guarantee**

Guarantee for a limited period, covering technical tools, devices and machines used under normal conditions. The length is given by the number after the letter M: 1 to 5 years

[>> Find out more](#)

**SAM Outillage**

10 rue Camille de RochetaillÃ©e  
42000 Saint-Etienne - France

RCS Saint-Etienne B 338 002 231 | SAS au capital de 8 189 583 Å,-

<https://www.sam-outillage.com/>

