

## RL.NANO-U1 | R.NANO-U1 - 1/4" INCH NANO SOCKETS SET



### Description :

Includes:

- 1 x 1/4" ratchet: RL.161.
  - 10 x 1/4" 6-point sockets - inch: 7/32' - 1/4' - 9/32' - 5/16' - 11/32' 3/8' - 13/32' - 7/16' - 1/2' - 9/16'.
  - 21 x standard series 1 bits - 1/4" - 6.35 mm drive - L 25 mm:
    - ES.T High Perf' for slotted head screw: F4.5 - F6.5 - F08.
    - EP.T High Perf' Phillips®: PH1 - PH2 - PH3.
    - ED.T High Perf' Pozidriv®: PZ1 - PZ2 - PZ3.
    - EH for 6-point countersunk screw: 1/4 - 1/8 - 3/16 - 5/32 - 7/32.
    - EXR Resistorx®: TR 10 - TR 15 - TR 20 - TR 25 - TR 27 - TR 30 - TR 40.
  - 1 x 1/4" socket holder bit: ECR.
  - 1 x 1/4" universal joint: R.240A.
  - 1 x 1/4" standard spring-clip bit holder: - R.235:
  - 1 x 1/4" short spinner: R.236C.
  - 1 x 1/4" standard extension - L 100 mm: R.210.
  - 1 x 1/4" standard extension - L 55 mm: R.206
  - Empty case: BV.RNANO-U.
- Weight: 0.81 kg.

### Informations :

	<b>RL.NANO-U1</b>
[kg]	0.250