



Cover frame fixed H: 1600 mm W: 800 mm

Model	
product brand name	SIVACON S4
product designation	masking frame
design of the product	fixed
Protection class	
protection class IP	IP30
suitability for use for outside use	No
Appearance	
color	light grey
Mechanical Design	
height	1 600 mm
width	800 mm
depth	80 mm
installation location	in the field
net weight	7 g
material	sheet-steel
Approvals Certificates	
General Product Approval	other

[Miscellaneous](#)



[Confirmation](#)

Environment

[Environmental Con-
firmations](#)

[Environmental Con-
firmations](#)

Further information

Information on the packaging

<https://support.industry.siemens.com/cs/ww/en/view/109813875>

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://mall.industry.siemens.com/mall/en/en/Catalog/product?mlfb=8PQ2000-8BA03>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/8PQ2000-8BA03>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8PQ2000-8BA03

last modified:

4/30/2025 

