

## UPT-20, 0...16 bar gauge, G1/2B , 4...20 mA, 2-W

### Universal process pressure transmitter UPT

Item number: 14091903

Quantity: 1 pcs.

Order code: UPT-20-ZZZ-KZPAS-BG416-GDZS2Z-ZZ  
PZZZZZZZZZZZZZZZZM1000Z-ZZFUP

Overview: UPT-20, 0...16 bar gauge, G1/2B , 4...20 mA, 2-W  
, 0.15%  
plastic case, plastic window PC  
without, M20x1.5 cable gland PA black 6-12mm  
Scaling: ...

Details: Universal process pressure transmitter UPT  
Model: UPT-20  
Specifications according to data sheet: PE 86.05  
power supply: DC 12...36 V / DC 14...30 V  
Measuring range: adjustable with turn down up to 100 : 1  
Ingress protection: IP 66/67 with pressure compensation  
Process connection type: Standard connection with pressure port  
Case design: plastic version, IP66/IP67  
Digital Display: without  
window: plastic window PC  
Output signal: 4 ... 20 mA, 2-wire  
Electrical connection: M20x1,5 / cable gland PA black (ø6-12mm)  
Measuring range: 0...16 bar gauge  
Process connection: G 1/2 B  
Accuracy: 0.15% of span  
Sensor principle: piezoresistiv