

Cisco SFP-10G-AOC3M Compatible SFP+ Active Optical Cable - 3 m (9.8 ft)

Product ID: SFP10GAOC3M



The SFP10GAOC3M is a Cisco SFP-10G-AOC3M compatible fiber optical SFP cable that is designed, programmed and tested to work with Cisco® brand 10 Gb compatible servers or routers and complies with MSA industry standards.

This active optical SFP cable (AOC) supports 10 GbE applications connected through SFP+ (Mini-GBIC) ports and is hot-swappable, making upgrades and replacements seamless by minimizing network disruptions. The AOC cable is lighter and more flexible than SFP+ direct-attach cables which makes it ideal for installation in tight spaces and over longer distances.

Designed for high-speed interconnects, this low-power, low-latency optical cable is ideal for applications such as point-to-point in-rack and across-rack network switch or server connections.

StarTech.com SFP Cables

All StarTech.com SFP & SFP+ cables are backed by a lifetime warranty and free lifetime multilingual technical support. StarTech.com offers a wide variety of direct-attach SFP cables and SFP modules, providing the convenience and reliability you need to ensure dependable network performance.

Certifications, Reports and Compatibility



Applications

- Use in 10Gb Ethernet network applications
- Point-to-point in-rack and across-rack server or network switch connections

Features

- 100% compatibility with Cisco SFP-10G-AOC3M guaranteed
- StarTech.com SFP cables are backed by a lifetime warranty
- Meets or exceeds OEM specifications and MSA (Multi-Source Agreement) industry standards
- Low power consumption of less than 1 W
- Hot-swappable

Hardware	Warranty	Lifetime
	Cable Jacket Type	PVC - Polyvinyl Chloride
	Compatible Brand	Cisco
Performance	Compatible Networks	10 Gbps
	Maximum Data Transfer Rate	10Gbps
Connector(s)	Connector A	1 - SFP+ Latching Plug
	Connector B	1 - SFP+ Latching Plug
Power	Power Consumption (In Watts)	< 1 W (per end)
Environmental	Operating Temperature	0°C to 70°C (32°F to 158°F)
	Storage Temperature	-40°C to 80°C (-40°F to 158°F)
Physical Characteristics	Cable Length	9.8 ft [3 m]
	Color	Black
	Product Height	0.5 in [1.2 cm]
	Product Length	9.8 ft [3 m]
	Product Width	0.6 in [14 mm]
	Weight of Product	2.3 oz [64 g]
Packaging Information	Package Height	0.4 in [10 mm]
	Package Length	12.8 in [32.4 cm]
	Package Width	9.7 in [24.7 cm]
	Shipping (Package) Weight	3.2 oz [90 g]
What's in the Box	Included in Package	1 - SFP+ cable
	Cable Type	Active Optical Cable

Product appearance and specifications are subject to change without notice.